

# Proline Prosonic Flow B 200

For reliable biogas flow measurement without compromises

## Process monitoring made easy

- Innovative measurement: industry-optimized ultrasonic flowmeter for measuring wet biogas, landfill or digester gas without pressure loss
- Broad range of applications: ideally suited for applications with fluctuating process conditions, low pressure and wet or dirty gases
- Easy and transparent energy balancing:
  - Direct measurement of the methane content ( $\text{CH}_4$ ) in the pipe
  - Calculation of additional characteristic values such as corrected volume, calorific value or Wobbe index
- Traceable measurement results: each device is tested on accredited calibration rigs (ISO/IEC 17025)
- Worldwide sales and service network with highly competent application consultants



# Proline

## simply clever

Process monitoring is becoming more demanding and the need for maximum product quality is steadily increasing. This is why Endress+Hauser continues to provide industry-specific flow measurement solutions optimized for future technology requirements.

The new generation of our Proline flowmeters is based on a uniform device concept. This means time and cost savings, as well as maximum safety over the entire plant life cycle.

**Consistent and uniform** Proline is a proven and uniform product concept, designed to do the same things the same way, thereby increasing the safety and efficiency of your operations.

**Optimal application solutions** Proline incorporates all modern flow measuring technologies, and thus optimizing plant up-time – true to our motto: “The industry-optimized flowmeter for your application.”

**Ingeniously simple** Proline is user-friendly through and through, ensuring that your process can be securely controlled with confidence.

## Added value in every respect



### HistoROM

- Automatic data storage ensures maximum plant safety
- Simple data restoration enables quick exchange of components
- Event logbook and data logger for quick failure analysis



### Simple operation

- Time-saving Endress+Hauser operating concept
- Optimal usability through guided parameterization
- User-specific menu structures and device access



### Seamless system integration

- Direct and transparent due to a wide range of fieldbuses
- Risk-free through extended host testing and certification
- Compatibility over the entire product life cycle enables device replacement without expert know-how



### W@M Life Cycle Management

- Open information system for device documentation and management
- Device-specific information for everyday work
- Quality of information unparalleled in scope and depth



## Prosonic Flow B 200

### Measure biogas without limitations

The biogas market is booming. No wonder, as the gas obtained from fermentation of energy crops, organic waste, liquid manure, sewage sludge or leftover plant materials can be used in a variety of beneficial ways – including refueling vehicles or generating heat and electricity in combined heat and power plants. For biogas plants to work properly, various process parameters have to be monitored around the clock: gas composition, pressure, temperature, and above all the produced gas quantity.

Prosonic Flow B 200 is an industry-optimized ultrasonic flowmeter that measures the volume flow of biogas, landfill or digester gas reliably and with high accuracy, even under greatly fluctuating operating conditions. Ultrasonic measurement has numerous benefits compared to conventional methods:

- Reliable measurement – high accuracy ( $\pm 1.5\%$ ) and a high operable flow range (30:1)
- Energy saving – no pressure losses
- Maintenance-free – no moving parts
- Space-saving – short inlet and outlet runs
- Wide range of uses – independent of the composition and the moisture of a gas
- Measurement possible even with minimum operating pressure





# Prosonic Flow B 200

## Advantages at a glance

### Simple operation

- Uniform Endress+Hauser operating concept
- Fast commissioning via guided configuration of parameters
- 17 display languages for use anywhere in the world
- Optimum process control due to simultaneous display of important characteristic variables, e.g. volume flow, calorific value, methane content, energy flow or temperature

### Secure data storage

- High plant availability through customer-friendly data-storage concept (HistoROM)
- No data loss – automatic storage of device data
- Fast restoration of device and configuration data for servicing
- Integral data logger for querying, monitoring and analysis of measured values
- Display module backup function, e.g. for the transfer of configuration data to other measuring points

### Maximum operational safety

- Fulfills all requirements of the biogas industry
- Permanent self-diagnosis and error monitoring
- Clear and unambiguous categorization of device or process errors
- Internationally recognized Ex approvals

### Seamless system integration / Life Cycle Management

- Seamless integration into existing process control systems, since it is a genuine two-wire device
- Tried-and-tested W@M information system:
  - Global access to all device information
  - Cost-effective support of business processes
- Compatibility between field device and process control system ensured at all times, as firmware/device drivers are available during the entire life cycle

### Industry-optimized sensors

- Robust sensor – reliable measurement of wet, dirty or corrosive gases
- Versatile mounting by means of lap-joint flanges
- Continuous measurement of the methane content ( $\text{CH}_4$ ) enables targeted reaction to problems in the process
- High measuring accuracy
  - Independent of the gas composition
  - Over the entire measuring range from 4 to 20 mA
- Trusted measurement results – each measuring device is tested on accredited, fully traceable calibration rigs (ISO/IEC 17025)



### Your benefits throughout the life cycle

- Maximum reliability in operation
- Minimum operating and maintenance costs
- Efficient process monitoring and energy balancing



## Reliable process control

### Direct methane (CH<sub>4</sub>) content measurement

Fermentation processes are not always uniform. The operating conditions, which in some cases fluctuate greatly, result in different levels of methane content (CH<sub>4</sub>) in the biogas, which have to be monitored constantly. With the Prosonic Flow B 200, it is now possible – using precisely measured sound velocity and an integrated temperature sensor – to simultaneously measure the methane content directly in the pipe, without the need for additional devices. This is a worldwide one-of-a-kind feature and opens up completely new perspectives for biogas plant operators:

- Continuous, around-the-clock monitoring of gas quantity and quality
- Fast and targeted reaction in case of interference in the fermentation process
- Efficient process control and energy balancing by calculating additional characteristic values such as:
  - Corrected volume
  - Calorific value
  - Wobbe index (indicates the quality of fuel gas)



## Two-wire technology at Endress+Hauser

Combining the benefits of the ultrasonic flow measuring principle with efficient two-wire technology no longer requires compromises. Prosonic Flow 200 enables seamless integration into existing plant systems along with tried-and-tested sensors:

- High operational safety in Ex areas due to intrinsically safe design (Ex ia)
- Reduced costs for installation and wiring
- Common installation practice

### Perfectly standardized

Uniform operation, menu structures, function designations, software, interfaces, data management, system integration, documentation, product structures, etc.

### High flexibility

Modular housing components and electronic modules

### Increased safety

Consistent implementation of all requirements of common industrial standards and recommendations

### Precise diagnostics

Clear categorization of device or process errors according to NE107: Maintenance/Out of specification/Function check/Failure

### Simply unforgettable

Customer-friendly data storage concept (HistoROM): back up, copy, compare or restore data

### Fulfills industry standards

Interference immunity, data retention, signal level, software, pressure equipment directive, self-monitoring, etc.



# Technical Data

Prosonic Flow 200 (transmitter)		Prosonic Flow B (sensor)	
Display	4-line, with push buttons or optical keys (Touch Control)	Nominal diameters	DN 50 to 200 (2 to 8")
Operation	<ul style="list-style-type: none"> <li>– Via the local display</li> <li>– Via operating tools, e.g. "FieldCare" from Endress+Hauser</li> </ul>	Process connections	Lap-joint flange: EN, ASME
Power supply	DC 18 to 30 V	Process pressure	10 bar
Ambient temperature	–40 to +60 °C (–40 to +140 °F)	Process temperature	0 to 80 °C (32 to 176 °F)
Degree of protection	IP66/67 (Type 4X enclosure)	Degree of protection	IP67 (Type 4X enclosure)
Design	Compact (aluminum or stainless steel housing)	Max. measured error	<ul style="list-style-type: none"> <li>– Volume flow: ±1.5% o.r. (from 3 to 30 m/s)</li> <li>– Methane content: ±2% o.f.s.</li> </ul>
Galvanic isolation	All circuits for outputs and power supply are galvanically isolated from each other	Operable flow range	30:1
Outputs	Current output (4–20 mA, HART) Pulse/frequency/switch output	Materials	1.4404/316L (stainless steel)
Communication	HART	Pressure loss	Negligible
Ex approvals	ATEX, IECEx, cCSAus	Approvals	PED
Ignition protection type	Intrinsically safe (Ex ia) Flame-proof (Ex d)		
		Subject to modification	

The Prosonic Flow B 200 measuring system fulfills the EMC requirements according to IEC/EN 61326 and NAMUR NE21. It also conforms to the requirements of the EU and ACMA directives and thus carries the **CE** and **UL** mark.

[www.addresses.endress.com](http://www.addresses.endress.com)

IN00025D/06/EN/03.14