Ultrasonic Level Measurement prosonic T FTU 230, FTU 231

Compact transmitter for non-contact limit detection in liquids and solids





















Applications

Prosonic T is a compact ultrasonic transmitter for non-contact level detection in applications such as conveyor belt delivery point monitoring, pump control, two-point control and distance measurement. With freely adjustable switching ranges from 0.25 m (0.8 ft) upwards, Prosonic T can also measure short distances.

- FTU 230
 - in coarse-grained solids (grain size from 4 mm/0.16 in) up to 2 m/6.6 ft in liquids up to 5 m/16.4 ft
- FTU 231 in coarse-grained sol
- in coarse-grained solids (grain size from 4 mm/0.16 in) up to 3.5 m/11.5 ft in liquids up to 8 m/26.2 ft

Features and Benefits


- Simple local pushbutton operation, with optional display
- Fully rotatable housing
- LEDs visible through housing cover allow quick monitoring of operational status
- \bullet Threaded connections from G $1^{1}\!/_{2}$ or $1^{1}\!/_{2}$ NPT
- Integrated temperature sensor for time-of-flight compensation
- Powered direct from mains with potential-free relay contact output




Measuring System

Application Examples:

- · Monitoring conveyor belts and belt
- delivery points Distance measurement
- Two-point pump control





Blocking Distance

Mounting with welded sleeve

E

Due to the ringing time of the sensor, there is a zone immediately below the sensor in which returning echoes cannot be detected. This so-called blocking distance determines the minimum distance between the sensor and the maximum product level.

The compact ultrasonic transmitter Prosonic T is a complete measuring point which can be calibrated and operated on-site without the need for additional equipment.

Installation

- Always mount the sensor such that the distance between it and the maximum product level exceeds the blocking distance.
- Never mount two Prosonic T in a vessel because the instruments may not function correctly.
- Do not mount the sensor in the centre of the vessel roof.
- Position the sensor at right angles to the surface of the material.
- Do not measure through the filling curtain.

Mounting on a Nozzle

The sensor must be mounted on a nozzle when the maximum level comes within the blocking distance.

- No build-up material should form in the nozzle.
- The inner surface of the nozzle should be as smooth as possible (no edges or welding seams).

	Mounting on a nozzle		
	Dimensions without Display D _{min} = 100 mm (3.9 in) L _{max} = 150 mm (5.9 in) Dimensions with Display		
	Sensor FTU	D mm (in)	max. L mm (in)
	230	50 (2)	80 (3.1)
	230	80 (3.1)	240 (9.4)
	230	100 (3.9)	300 (11.8)
	231	80 (3.1)	240 (9.4)
, D	231	100 (3.9)	300 (11.8)

Mounting examples

Mounting on a Nozzle The recommend nozzle dimensions are limits, within which the nozzle can vary. Check that the nozzle diameter is large enough, but keep the nozzle length to a minimum.

Operation

Operation via Display

The plug-in display allows access to the Endress+Hauser operating matrix. With only a few settings

Mounting

with counter nut

L


The

- selection of application parameter • assignment of relay switch points
- the device is ready to measure.

Operation without Display

The basic functions of the Prosonic T can be set by using just the four pushbuttons –, +, V, H on the front panel of the instrument. Functions:

- Setting relay switch points,
- Parameter protection by entry locking.



Technical Data

Function

Operation and System Design

Input Variables

Output Variables

Relay

Measuring Accuracy

Application Conditions

¹⁾ Please check with Endress+Hauser before using transmitters at higher temperatures and pressures.

When transmitters are subjected to high temperatures and pressures (with limiting conditions), it is recom-mended that the coupling (process connection) be tightened.

Mechanical Construction

Display and Operating Elements


Power Supply

Supplementary Documentation

Electrical Connection

Manufacturer	Endress+Hauser			
Instrument designation	Prosonic T			
Others	CE mark			
Non-contact limit detection in liquic	Is and coarse-grained bulk solids			
Measuring principle	Ultrasonic level measurement, time-of-flight measurement			
Modularity	Compact ultrasonic sensor, with optional display			
Signal transmission	Relay			
Measured variable	Limit, determined from distance between the transmitter and material			
Measuring range	FTU 230: 0.255 m (0.816.4 ft) FTU 231: 0.48 m (1.326.2 ft)			
Blocking distance	FTU 230: 0.25 m (0.8 ft) FTU 231: 0.4 m (1.3 ft)			
Frequency	FTU 230: approx. 70 kHz FTU 231: approx. 50 kHz			
Pulse frequency	0.53 Hz, depending on sensor			
Delay time	approx. 1 s			
Version	Single-pole changeover contact, potential-free for limit detection			
Switching capacity	5 A; 250 V _{AC} , 100 V _{DC} ; 600 VA at $\cos \phi$ =1, 300 VA at $\cos \phi$ =0.7			
Fail-safe mode	Min., max. and hold; Default: The relay is de-energised, when the echo is lost			
Switching time	1255 s			
Hysteresis	Adjustable 0100%			
Reference conditions	Ideal reflection from calm. flat surface at 20°C (68°F)			
Measuring uncertainty	0.25% for maximum measuring span			
Resolution	2 mm (0.08 in)			
Orientation	Vertical to the surface of the product, not mounted centrally in the vessel			
Medium temperature range 1)	-40+80°C (-40+176°F) (built-in temperature sensor)			
Operating temperature range (electronics)	-20+60°C (-4+140°F)			
Storage temperature range	-40+80 °C (-40+176°F)			
Operating pressure p _{abs.} 1)	3 bar (43.5 psi)			
Climatic class	DIN / IEC 68 T2-30 Db			
Type of protection (EN 60529)	IP 67(NEMA 6), with housing cover open IP 20			
Vibration resistance	DIN IEC 68 T2-6 Tab.2.C (1055 Hz)			
Electromagnetic compatibility	Interference emission to EN 61326, Electrical Equipment Class B Interference immunity to EN 61326, Annex A (Industrial) and NAMUR Recommendation NE 21 (EMC)			
Certificates	Standard			
Design	Compact instrument, installed with box spanner 60 AF max. torque: 1520 Nm (11.114.8 ft lbs)			
Dimensions	See »Dimensions« page 4			
Material	See »Dimensions« page 4 Housing: PBT (fibre-glass reinforced, flame-retarded) Threaded boss and sensor: PVDF			
Seals	Internal between threaded boss and sensor: EPDM seal External on the threaded boss: EPDM seal			
Process connection	FTU 230: Thread G 1 ¹ / ₂ or 1 ¹ / ₂ or 11.5 NPT FTU 231: Thread G 2 or 2 - 11.5 NPT			
Cable entry	Pg 16, cable diameter 59 mm (0.20,35 in) Sleeves for connection thread G ¹ / ₂ and ¹ / ₂ NPT M 20x1.5 available			
Cable	Standard installation cable			
Display (LCD)	4 character display Dimensions: L x B x H: 40 x 20 x 10 mm (1.6 x 0.8 x 0.4 in)			
LEDs (visible from outside)	Red: indicates fault and switching status of relay Green: Indicates power on and entry acknowledgement			
AC voltage	180250 V _{AC} ; 90127 V _{AC}			
Power consumption	< 4 VA			
Switch-on current Electrical isolation	100 mA, pulse width half life time 70 ms Isolation between evaluation electronics and power supply terminals			
- Prosonic T System Information SI 021F/00/en				


Prosonic T System Information SI 021F/00/en
Prosonic T Compact transmitter for continuous, non-contact level measurement Technical Information TI 246F/00/en




FTU 230, FTU 231 • 4-wire

· Separate power supply 230 V_{AC} and 115 V_{AC}

Dimensions



Accessories




Display

• Order No.: 942663-0000

Adapter Flange FAU 70 E/A

• Order No.: 942636-XXXX



Endress+Hauser GmbH+Co. KG Instruments International P.O. Box 2222 D-79574 Weil am Rhein Germany

Tel. (07621) 975-02 Fax (07621) 975-345 http://www.endress.com info@ii endress.com



Cable entry: Pg 16, cable diameter 5...9 mm

Dimensions Prosonic T

Threaded versions

sleeves for connecting threads G 1/2; 1/2 NPT; M 20x1.5 supplied

9

Others

Product designation

When mounting in tapped holes to DIN 3852 Part 2, check that the recese diameter d₄ is »wide«.

Product Structure