

N

 \triangleright

ω

O

Installation Notes TMT 180

- The head transmitter must be installed in accordance with this control drawing and Article 504 and 505 of NEC and Section 18 of CEC as applicable.
- The spacing between intrinsically safe and non intrinsically safe circuits is at least 50 mm.
- Use supply wires suitable for 5°C above
- The configuration of the transmitter TMT 180 is only permitted in non hazardous locations using the TMT 181A.
- To prevent ignition of explosive atmospheres, disconnect power before servicing.
- The device must be installed in a suitable enclosure.
- Warning: Substitution of components may impair suitability for Class I, Division 2.

NONINCENDIVE

NI Class I / Div. 2 / Groups ABCD

Oi

O

 \triangleright

œ

0

- Depending on location install per National Electrical Code (NEC) using wiring methods described in article 500 through article 510 and Section 18 of CEC.
- The transmitter TMT 180 and RTD Sensor is to be installed in Class I, Division 2 location.
- Intrinsic safety barrier not required. Vmax ≤ 30 V DC.
- Warning: Do not disconnect equipment unless power has been switched off or the area is known to be nonhazardous.
- Nonincendive field wiring installation

The Nonincendive Field Wiring Circuit Concept allows interconnection of Nonincendive Field Wiring Apparatus with Associated Nonincendive Field Wiring Apparatus or Associated Intrinsically Safe Apparatus or Associated Apparatus not specifically examined in combination as a system using any of the wiring methods permitted for unclassified locations, when $Voc \le Vmax$, $Ca \ge Ci + Ccable$, $La \ge Li + Lcable$.

Transmitter Nonincendive Field Wiring parameters are as follows:

Ui or Vmax $\leq 30 \text{ V DC}$ Ci $\leq 144 \text{ nF}$

Li ≤ 0

For these current controlled circuits, the parameter Imax is not required and need not to be aligned with parameter Isc and It of the Associated Nonincendive Field Wiring Apparatus or Associated Apparatus.

4

Functional ratings

These ratings do not supersede Hazardous Location values

Unom ≤ 35 DC Inom ≤ 4 to 20 mA

	Approved Pfanzelt	Date (yyyy-mm-dd) 2005-08-25	Drawing No. 14 13 00 112	Dwg.rev.	Revision no.	Revision date (yyyy-mm-dd)	Name	Material 7 ² ZD 051R/09/6	1021424 en/12.05	Endress+Hauser 🖽
Volume (mm³)	Designed Pfanzelt	Date (yyyy-mm-dd) 2005-08-29	iTEMP TMT 180	Scale 1:1	CONTRO	L DRAWING	Serie	s		
Refer to protection notice ISO 16016	Edge of working parts ISO 13715	Geometrical tolerancing ISO 2768-mH-E	Part No.	Format A4	Nonincen	dive		Objekt version		Endress + Hauser Wetzer GmbH+Co. KG Nesselwang / Germany

ယ