Technical Information TI161F/00/en

Operating Instructions 017189-1000

Capacitance Level Measurement *Probes 11500 Z, 11500 ZM*

Ceramic, fully insulated rod probes for high temperatures and pressures





















Versions

Four basic versions, each with its own variations, cover all applications:

- 11500 Z with threaded boss
- 11500 Z with flange
- 11500 ZM with ground tube and threaded boss
- 11500 ZM with ground tube and flange The versions with ground tubes are especially designed for electrically non-conductive liquids with low dielectric constants.



Application

Continuous level measurement and limit detection in liquids.

The probes are designed for use in tanks with

- very high pressures (up to 500 bar)
- very high temperatures (up to 400°C).
- For use in steam: depending on the resistance of Al2O3 (99.7%)

They are also approved for use in explosion-hazardous area Zone 0.



Measuring System

A complete measuring system consists of the probe, electronic insert and the level transmitter FMC. or level limit switch FTC...


At low ambient temperatures the electronic insert can be mounted in the probe head housing. Separate mounting is required at high temperatures.

Overspill protection

The probe can be used as overspill protection for water polluting liquids.

For approved combination of instruments, see section on "Certificates".

When to install an electronic insert



Mounting for Limit Detection

Mounting from the side

- When the probe is mounted from the side, the Nivotester always accurately switches at the limit point specified by where the sensor is installed.
- For recommended probe lengths please refer to Page 7.
- For applications with organic materials, a probe with ground tube is recommended in order to produce large capacitance changes with small dielectric constants.
- If the probe is mounted from the side, then it should be tilted slightly downwards so that the liquid can flow off more easily (and out of the ground tube, if used) and prevent build-up. The ground tube is not suitable for viscous products or those causing
- Only short probes (max. 500 mm) may be mounted from the side if no ground tube is used.


Mounting from above


• If the probe is mounted from above, then the switchpoint may be varied by adjusting the setting on the Nivotester.

300

400

- Note: A probe with a ground tube is recommended for use with organic materials.
- This kind of probe is also recommended for applications with strong turbulence.
- Please refer to Page 7 for minimum lengths when mounting from above. As the capacitance can be adjusted within a very wide range, it is useful to select a probe which is somewhat longer than required.





Mounting for Continuous Measurement


- Mount the probe vertically in the tank from above.
- The probe without the ground tube 11500 Z is for use with electrically conductive liquids.
- If turbulence is present, then a side bracket (insulated if possible) is to be used if the probe is longer than approx. 500 mm.
- The 11500 ZM probe with ground tube is more suitable for turbulent liquids which do not cause build-up.
- Use the 11500 ZM probe with ground tube for organic substances and other electrically non-conductive liquids.



Centre:

Process tank with turbulence and build-up. The probe 11500 Z with bracket should be used

Right: Process tank with turbulence but without build-up. The probe 11500 ZM should be used



Several Measuring Points

For capacitive level limit detection or continuous level measurement, probes without ground tubes should not be too close to each other if mounted in a metal tank or in neighboring plastic tanks.

This is to ensure that no mutual interference can occur. Please contact Endress+Hauser if they are mounted at intervals of less than 500 mm.

Transport Unpacking Mounting

Transport

The probe can be transported without the risk of breaking because:

The probe consists of a ceramic tube surrounding a metal unit.

The ceramic tube is resistant to many chemicals and withstands extremely high temperatures and pressures.

Bending or hitting the probe, however, can result in breaking the ceramic and

therefore damaging the insulation.

Unpacking

Compare the code on the nameplate of the probe with the order number on Page 6 to ensure that the correct probe has been delivered.

Remove the packing on-site just before mounting.

A different method of packing is used for each version:

Probe with ground tube 11500 ZM The ground tube is an integral part of the measuring system and is not to be unscrewed!

The ground tube is filled with a plastic granulate (Noryl, PPO).

- Open the plug at the lower end of the ground tube and allow the granulate to run out. Do not hit the ground tube!
- Remove the adhesive tape from the vents situated at the top of the ground tube
- Blow or rinse out the ground tube if the probe has to totally clean before mounting.

Probe without ground tube 11500 Z The probe rod is protected by a metal tube which is filled with a plastic granulate (Noryl, PPO).

- Loosen the screw cap (55 AF) at the bottom of the protective pipe
- Unscrew the cap only at the place of mounting and allow the plastic granulate to run out from the protective pipe.

Do not hit the protective pipe!

Probes with a threaded boss

- Hold the slip-on nut with a pipe wrench and begin to turn the probe with a 60 AF open-ended spanner at the hex nut.
- Note that the length of the thread of the boss is approx. 30 mm. Remove the probe from the protective pipe by carefully turning it by hand as you come to the end of the thread.

Probes with a flange ≥ DN50

At the bottom on the flange is a short threaded pin (approx. 5 mm) onto which the protective pipe is screwed.


 Carefully unscrew the probe and flange from the protective pipe by hand.

Probes with a flange < DN50

A counter flange is welded onto the protective tube.

 Remove the mounting screws from the flange and counter flange and make sure that the two flanges do not move in relation to one another until you have carefully removed the probe from the protective pipe.

Avoid hitting or putting any strain on the ceramic rods when removing the probe from the protective pipe.



Mounting

- Ensure that the ceramic rods are in good order (no cracks or chipping) and check the probe length.
- The probe rod must not be shortened otherwise the insulation will be damaged and its resistance to chemical corrosion will be lost.
- Mount the probe immediately after unpacking.
- Please note instructions given in the certificates.
- Use a suitable seal for the application
- Avoid hitting or putting any strain on the probe (especially with the probe 11500 Z) when sliding it through the threaded sleeve or the collar with counterflange or when screwing it tight.

Short-term storage

If the probe has to be stored, then lay it vertically with the probe head downwards and secure to prevent it falling over.

The probe should be repacked if it is to be stored or transported for any long period of time!

Carefully remove the packing!
The diagrams show the probe 11500 Z with threaded boss, but without the ground tube

Connection

Please refer to the Technical Information about the electronic insert EC... for the electrical connections when installing the electronic insert in the probe head.


No moisture must enter the probe head housing during storage of the probe, connection of the electronic insert or during operation.


The housing cover and the cable gland must be screwed tight.

Technical Data


Operating data

- Relationship between maximum operating pressure and temperature: refer to diagram on the right.
- Resistance to temperature shock: 150°C/min
- For use in steam: depending on the resistance of Al2O3 (99.7%)





Capacitance of the probe



Lateral load on the probe at 20°C and static loading

Probe lengths

Minimum: 100 mm Maximum: 2000 mm

Probe length tolerances:

Probe length Tolerance + 0 mm, - 5 mm to 1 m to 2 m + 0 mm, -10 mm

Process connections:

- Thread G 11/2 A DIN/ISO 228 Sealing conf. to DIN 3852 Z, Page 2, Form D, large sealing ring conf. To DIN 7603, Form D (recommended material: soft iron)
- DIN flange: DIN 2501, Page 1


• ANSI flange: ANSI B 16.5 High pressure flange: on request


Materials:

- Full rod insulation: approx. 2 mm ceramic Al2O3
- Ground tube: stainless steel 1.4301 or 1.4571 (11500 ZM)
- Spacer: PTFE (11500 ZM), temperature resistant up to 200°C
- Threaded boss G 11/2: 1.4571
- Flange: steel, primed, or stainless steel 1.4571
- Pipe between process connection and housing: stainless steel 1.4571
- · Cable glands:
- Standard PG in nickel-plated brass with NBR sealing for cable diameter 7...10 mm, Protection: IP55 Ambient temperature up to 100°C
- Water-tight PG in polyamide with neoprene CR sealing for cable diameter 5...12 mm. Protection: IP66 Ambient temperature max. 80°C

Subject to modification

Dimensions and Probe Length






Probe 11500 Z with threaded boss G 1½

Probe 11500 Z with flange * Threaded ledge for flanges \geq DN45, ANSI 2"

Material characteristics, relative dielectric constant ε_{r}	Limit detection, mounting from the side	Limit detection, mounting from above
	Recommended total length L	The lengths given here in this table incorporate the additional minimum lengths from the sealing surface of the flange or threaded boss right up to the limit point required.
electrically conductive	100 mm	50 mm
$\varepsilon_r > 10$ e.g. alcohols	150 mm	100 mm
ε_r approx. 410	200 mm	200 mm
ε_r approx. 34		400 mm
ε_r approx. 24 e.g. oils	400 mm	

Please contact us if the dielectric constant of the material is not known.




Continuous level measurement

How to Order

Rod probe 11500 Z Certificate ATEX II 1/2 G, EEx ia IIC T6, WHG Note safety instruction (XA) for electrostatic charging! ATEX II 1/2 G, EEx ia IIC T6 Note safety instruction (XA) for electrostatic charging! For non-hazardous areas Special version ATEX II 1/2 G, EEx ia IIB T6 ATEX II 1/2 G, EEx ia IIB T6, WHG ATEX II 3 G, EEx nA II T6 For use with (label text) C FTC 470/471 Z with EC 17 Z, 2-wire PFM FMC 470 Z with EC 47/37 Z, 2-wire PFM FMC 671 Z with EC 47/37 Z, 2-wire PFM FMC 672 Z with EC 47/37 Z, 2-wire PFM FMC 676 Z with EC 47/37 Z, 2-wire PFM FMC 677 Z with EC 47/37 Z, 2-wire PFM with EC 17 Z, 2-wire PFM, not WHG with EC 17 Z, 2-wire PFM, not WHG FMC 671 Z FMC 676 Z FTC 625 with EC 17 Z, 2-wire PFM with EC 27 Z, 2-wire PFM FTC 625 for use with unspecified instrument Special version Process connection, material Thread ISO228, G2 G $1^{1}/_{2}$ A, 316Ti H2 1" NPT, Thread ANSI, 316Ti DN50 PN 10/16 B, Flange DIN 2527, K1 steel 316Ti DN50 PN 10/16 B, Flange DIN 2527, K2 DN80 PN 10/16 B, Flange DIN 2527, M1 steel DN80 PN 10/16 B, Flange DIN 2527, M2 316Ti DN100 PN 10/16 B, Flange DIN 2527, P1 steel P2 DN100 PN 10/16 B, Flange DIN 2527, 316Ti 150 lbs RF, 150 lbs RF, Ω1 Flange ANSI B16.5, steel Ω2 Flange ANSI B16.5, 316Ti 4", Flange ANSI B16.5, R1 150 lbs RF. steel 4" Flange ANSI B16.5, 316Ti R2 150 lbs RF, Special version Y9 Rod material Rod: Ceramic insulation, 304 Special version Probe length Lmm (100...2000 mm), total length 9 Special version Housing C Aluminium, E-Housing IP66, NPT 1/2" Aluminium, E-Housing IP66, Aluminium, E-Housing IP66, Aluminium, E-Housing IP66, $G^{1}/_{2}A$ M20 HNA24 gland Ctd. alum., C-Housing IP66, NPT $^{1}/_{2}$ " Ctd. alum., C-Housing IP66, G $^{1}/_{2}$ A Ctd. alum., Ctd. alum., Ctd. alum., Ctd. alum., C-Housing IP66, HNA24 gland Special version Electronic insert A electronic insert not installed with EC 17 Z, 2-wire PFM D with EC 27 Z, 2-wire PFM G with EC 37 Z, 2-wire PFM, 33 kHz H with EC 47 Z, 2-wire PFM, 1 MHz Special version 11500 Z Order code Please state length of probe in mm See also section "Probe Length"

Dimensions and Probe Length




ø84 Cable gland, see ca. 250 Order key ø60 Flange, see Order key Vent L min. 100 L max. 2000 Probe rod Ground tube Spacer ø max. 43

Probe 11500 ZM with ground tube and threaded boss G 1½

Probe 11500 ZM with ground tube and flange

Material characteris relative dielectric co		Limit detection, mounting from the side	Limit detection, mounting from above
		Recommended total length L	The lengths given here in this table incorporate the additional minimum lengths from the sealing surface of the flange or threaded boss right up to the limit point required.
electrically conduct	ive	(approx. 100 mm)	50 mm
$\varepsilon_r > 10$	e.g. alcohols	100 mm	50 mm
ε_r approx. 410		100 mm	100 mm
ε_r approx. 34			200 mm
ε_r approx. 24		200 mm	
ε_r approx. 2	e.g. Oils, benzine		250 mm
ε_r approx. 1,52	e.g. propane	300 mm	300 mm

Please contact us if the dielectric constant of the material is not known.



Continuous level measurement

How to Order

```
Rod probe 11500 ZM
              Certificate
                  ATEX II 1/2 G, EEx ia IIC T6, WHG
ATEX II 1/2 G, EEx ia IIC T6
                  Special version
                  ATEX II 1/2 G, EEx ia IIB T6
ATEX II 1/2 G, EEx ia IIB T6, WHG
                  ATEX II 3 G, EEx nA II T6
                  For use with (label text)
                  C FTC 470/471 Z with EC 17 Z,
                                                        2-wire PFM
                      FMC 470 Z
                                       with EC 47/37 Z, 2-wire PFM
                  G FMC 671 Z
                                       with EC 47/37 Z, 2-wire PFM
                                       with EC 47/37 Z, 2-wire PFM with EC 47/37 Z, 2-wire PFM
                      FMC 672 Z
                      FMC 676 Z
                      FMC 677 Z
                                       with EC 47/37 Z, 2-wire PFM
                                       with EC 17 Z, 2-wire PFM, not WHG with EC 17 Z, 2-wire PFM, not WHG
                      FMC 671 Z
                      FMC 676 Z
                                       with EC 17 Z, 2-wire Privi
with EC 17 Z, 2-wire PFM
                      FTC 625
                      FTC 625
                      for use with unspecified instrument
                      Special version
                      Process connection, material
                      G1 G 1^{1}/_{2} A,
G2 G 1^{1}/_{2} A,
                                                   Thread ISO228,
                                                   Thread ISO228,
                                                                            316Ti
                            DN50 PN 10/16 B, Flange DIN 2527,
                      K1
                                                                            steel
                            DN50 PN 10/16 B, Flange DIN 2527,
                      K2
                                                                            316Ti
                            DN80 PN 10/16 B, Flange DIN 2527,
                      M1
                                                                            steel
                      М2
                            DN80 PN 10/16 B, Flange DIN 2527,
                                                                            316Ti
                            DN100 PN 10/16 B, Flange DIN 2527,
                      P1
                                                                            steel
                      P2
                            DN100 PN 10/16 B, Flange DIN 2527,
2", 150 lbs RF, Flange ANSI B16.
2", 150 lbs RF, Flange ANSI B16.
                                                                            316Ti
                      Q1
                                                   Flange ANSI B16.5,
                                                                            steel
                           2",
                       Q2
                                                   Flange ANSI B16.5,
                                                                            316Ti
                            4",
                      R1
                                     150 lbs RF,
                                                   Flange ANSI B16.5,
                                                                            steel
                            4".
                                                   Flange ANSI B16.5,
                                     150 lbs RF,
                      R2
                                                                            316Ti
                            Special version
                       Y9
                            Rod material and ground tube
                                Rod: Ceramic insul., ground tube,
                                                                            304
                                Rod: Ceramic insul., ground tube,
                                                                            316Ti
                                Special version
                                Probe length L
                                     .....mm (100...2000 mm), total length
                                     Special version
                                     Housing
                                        Aluminium, E-Housing IP66, NPT 1/2"
                                         Aluminium,
                                                        E-Housing IP66,
                                         Aluminium,
                                                        E-Housing IP66,
                                                                            M20
                                         Aluminium,
                                                        E-Housing IP66,
                                                                            HNA24 gland
                                         Ctd. alum.,
                                                        E-Housing IP66,
                                                                            NPT 1/2"
                                     U Ctd. alum., E-Housing IP66,
                                                                           G^{1}/_{2}A
                                         Ctd. alum.,
                                                        E-Housing IP66,
                                                                           M20
                                     W
                                         Ctd. alum.,
                                                       E-Housing IP66, HNA24 gland
                                         Special version
                                         Electronic insert
                                         A electronic insert not installed
                                        C with EC 17 Z, 2-wire PFM D with EC 27 Z, 2-wire PFM
                                        G with EC 37 Z, 2-wire PFM, 33 kHz
H with EC 47 Z, 2-wire PFM, 1 MHz
                                            Special version
11500 ZM
                                                   Order code
                                                   Please state length of probe in mm
                                                    See also section "Probe Length"
```


Accessories

Protective cover

for aluminium housing Material: polyamide

Maximum ambient temperature: 100°C

The protective cover should be used when mounting in the open. This protects the probe with aluminium housing from excessive temperatures and condensation caused by large temperature variations.



Supplementary Documentation

- □ Electronic Insert EC 17 Z
 Technical Information TI 268F/00/en
- □ Nivotester FTC 470 Z, FTC 471 Z Level limit switch Technical Information TI 088F/00/en
- Electronic Insert EC 37 Z, EC 47 Z Technical Information TI 271F/00/en
- □ Silometer FMC 470 Z
 Level measuring instrument
 Technical Information TI 018/00/en
- □ Contacter HTA 470 Z
 Limit signal transmitter
 Technical Information PI 011/00/en

Further instruments for limit detection and continuous level measurement on request.

Certificates

Order Details

- □ Order code
- □ Probe length

- Special version as required
- □ Accessories (e.g. protective cover)

Endress+Hauser GmbH+Co. Instruments International P.O. Box 2222 D-79574 Weil am Rhein Germany

Tel. (07621) 975-02 Tx 773926 Fax (07621) 975345 http://www.endress.com info@ii.endress.com



01.99/MTM

