

Technical Information Omnigrad S TR63

RTD thermometer EEx-d or EEx-ia certified, replaceable insert, thermowell from pipe, process connection threaded, flanged or sliding. PCP (4...20 mA), HART® or PROFIBUS-PA® electronics



Range of uses

The Omnigrad S TR63 is an RTD industrial thermometer with a inset (Pt100) and threaded or flanged thermowell from pipe. It is developed for the use in the chemical, petrochemical and energy industries, but suitable also for other generic applications.

In compliance to EN 50014/18/20 (ATEX certification) it is therefore particularly suitable also for hazardous areas.

When required, it's also available with a transmitter (PCP, HART $\ensuremath{\mathbb{R}}$ or PROFIBUS-PA $\ensuremath{\mathbb{B}}$) into the housing.

The process connection of the thermowell is threaded or flanged in compliance to the standard of process requirements.

Application areas

- Chemicals industry
- Energy industry
- Gas Processing industry
- Petrochemical industry
- General industrial services

Features and benefits

- Several types of process connection
- Several type of materials available for the thermowells
- Customized immersion length
- Aluminium housing, with protection grade from IP66 to IP68
- Mineral oxide replaceable insulated insert (MgO), diameter 3 or 6 mm
- PCP, HART® and PROFIBUS-PA®, (4...20 mA 2-wire transmitters)
- The accuracy of the sensing element (Pt100) is: class A or 1/3 DIN B (IEC 60751) with electrichal connection to 2, 3 or 4 wires
- The sensing elements (Pt100) are available in wire-wound WW (range:-200...600°C) or thin-film TF (range:-50...400°C) with single or double Pt100 execution
- ATEX II 1 GD EEx-ia IIC certification
- ATEX II 1/2 GD EEx-ia IIC certification
- ATEX II 1/2 GD EEx-d IIC certification
- ATEX II 2 GD EEx-d IIC certification

C E 🖾



Function and system design

Measuring principle

The RTD (Resistance Temperature Detector), is a sensor where the electrical resistance varies with the tem perature. The material of the RTD is Platinum (Pt) with a value of the resistance (R), referred to a nominal value at the temperature of $0^{\circ}C = 100,00 \Omega$ (in compliance to rule IEC 60751; it is called Pt100). The very important is to define the RTD; it is defined with a standard " α " value measured between $0^{\circ}C$ and $100^{\circ}C$. This value is: $\alpha = 3.85 \times 10^{-3} \circ C^{-1}$.


The temperature is measured indirectly by reading the voltage drop across the sensing resistor in the presence of a constant current flowing through it using Ohm's. The measuring current should be as small as possible to minimise possible sensor selfheating; normally this current is around 1mA, no higher.

The resistance value measured for each degree is about = 0,391 Ohm/K; over 0°C it is opposite proportional at the temperature. The standard RTD connection at the plant instrument can be to 2, 3 or 4 wires to simple or double RTD element.

Equipment architecture

The construction of the TR63 temperature sensor is based on the following standards:

- EN 50014/18 (housing)
- Neck (1 or 2 nipple and 1 "3 union", standard or EEx- execution)
- IEC 60751 (insert and sensing element).
- Pipe thermowells standard like: ENI, MONTEDISON, ENEL, ecc.



The housing is in painted aluminium alloy; it is suitable to contain a transmitter and/or the ceramic block of the insert; the "Ingress Protection" is from IP66 to IP68. The neck composed by one or two nipple and one "3 union", standard or EEx- execution, it is the extension

between the head and the thermowell. The insert diameter is 3 - 6 mm, is composed by MgO cable (SS 316L sheath) with a sensing element (Pt100

ohm/0°C) positioned at the MgO cable tip. The standard electrical connection is to 2, 3 or 4 wires for sensing element (Pt100).

The thermowell is from bar stock, with execution, on wetted part, conical, straight or tapered.

The process connection on the thermowell is: threaded or flanged, in some case it can be to weld also.

Fig. 1: TR 66 with the various types of process connections and end parts of the probe

M	-		1	Г	
Material & Weight	Housing	Insert	Neck	Thermowell	Weight
	aluminium epoxy coated	sheath in SS	nipple and 3 union:	thermowells: SS 316/1.4401, SS	From 1.5 to 5.0
		316L/1.4404	SS 316/1.4401,	446/1.4749 Inconel 600	kg for standard
			A105		options

Performance

Operating conditions	Operating condition or test	Product type or rules		Value or data of test			
	Ambient temperature	housing (without head-mounted tr	ansmitter	-40÷130°C			
		housing (with head-mounted trans	mitter)	-40÷85°C			
	Process temperature	Same of measurement range (see below).					
	Maximum flow velocity	The maximum flow rate tolerated by the thermowell decreases as the immersion length increases (U). The methods used to verify the resistance of thermowells with pressure, temperature and flow rate data can also be compliant with those indicated in standard ASME/ANSI PTC 19.3. For assistance on resistance tests, please contact the E+H Customer Service Department.					
	Shock and vibration resistance	RTD Inset in according to the rule	Acceleration	3 g of peak			
	test	IEC 60751:	Frequency	from 10Hz to 500Hz and back			
			Time of the test	10 hours			

Fig. 2: Operating conditions

асу	RTD maximum	error type TF -	DIN-IEC-EN 60751						
	Cl. A	$3\sigma = 0.15+0.$ $3\sigma = 0.30+0.$	0020Itl	= -50250°C = +250400°C	2,0 Class B (*C) 1,5				
	Cl. 1/3 DIN B	$3\sigma = 0.10+0.$ $3\sigma = 0.15+0.$ $3\sigma = 0.15+0.$ $3\sigma = 0.30+0.$	0020ItI 0020ItI	= 0100°C = -500 = 100250°C = 250400°C	200 -100 0 100 200 300 400 500 600 C				
	$\pm 3\sigma = range inclusion$	1ding 99.7% of th	ne readings. (t = absolute value of the ten	nperature in °C).				
	RTD maximum	RTD maximum error type WW - Range: -200 to 600°C							
	Cl. A	$3\sigma = 0.15 + 0.$	0020Itl	= -200600°C					
	Cl. 1/3 DIN B	$3\sigma = 0.10+0.$ $3\sigma = 0.15+0.$ $3\sigma = 0.15+0.$	0020ItI	= -50250°C = -20050 = 250600°C	200 -100 0 100 200 300 400 500 6000				
	$\pm 3\sigma$ = range inclu	$\pm 3\sigma$ = range including 99.7% of the readings. (t = absolute value of the temperature in °C).							
	Others errors								
	Transmitter maxi	mum error	See the co	rresponding documentation (codes at the end of the document)					
	Display maximum		0.1% FSR -	200)					

The "4 wires" configuration, is provided as a standard connection for the single Pt 100's excludes additional errors in every condition. Generally in the "4 wires" configuration there is a higher guarantee of accurancy.

Response time	Tests, with the RTD insert, in	Tests, with the RTD insert, in water at 0.4 m/s (according to IEC 60751); from 23 to 33°C:							
	Stem diameter of the insert	Sensing element type	Time for 50% or 90% of	Response time					
			temperature step						
	6 mm	TF / WW	t ₅₀	3.5 s					
			t ₉₀	8.0 s					
	3 mm	TF / WW	t ₅₀	2.0 s					
			t ₉₀	5.0 s					
Insulation	Measurement Insulation type		Result						
	Insulation resistance between ter	minals and probe sheath	above 100 M Ω at 25°C						
	According to IEC 60751, test vol	tage 250 V	above 10 M Ω at 300°C						
	ų								

Self heating

Negligible when the E+H iTEMP $\ensuremath{\mathbb{B}}$ transmitters are employed.

Installation

The TR63 can be installed on pipes or tanks by means of threaded or flanged connections. The counterparts for process connections and gaskets, when required, are not supplied with the sensor and must be purchased separately by the user. The immersion length must take into account all the parameters of the thermometer and the process to measure. If the immersion is too low, an error may be generated in the temperature recorded due to the lower temperature of the process fluid near to the walls and heat transfer, which takes place through the sensor stem. The incidence of such an error can be not negligible if there is a big difference between the process temperature and the ambient temperature. To prevent measuring errors of this kind, it is advisable to use thermowells with a small diameter and an immersion length (L) of at least $100 \div 150$ mm. In small section ducts the tubing's axis must be reached and preferibly slightly exceeded by the tip of the probe (see fig. 3A-3C). Insulation of the outer part of the sensor reduces the effect produced by a low immersion. Alternatively, it is also possible to adopt a tilted installation (see fig. 3B-3D).





Fig. 3: Installation examples

For a best installation, in the industries, it's better to follow the rule: $h \simeq d$, L > D/2 + h. As far as corrosion is concerned, the base material for parts in contact with the fluid is able to withstand the most common corrosive agents up to the highest temperatures. Even the nipples and 3 elements coupling supplied with the connection fitting of the instrument are able to withstand a wide range of aggressive substances. For further information on specific applications, contact the E+H Customer Service Department. Disassembled components of the sensors must be reassembled with the recommended clamping torques in order to ensure the appropriate IP protection class within the sensor-housing coupling. In the case of vibrations the thin film sensing element Pt100 (TF) may offer advantages; the wire wound Pt100 (WW), besides having a larger measurement and accuracy range, guarantees greater long term stability.

System components

Housing

The protection housing, our "TA21H", commonly referred to the "connection head", is used to contain and protect the terminal block or the transmitter and to join the electric connections to the mechanical component.



The TA21H used for the TR65 is compliant with EN 50014/18 and EN 50281-1-1, EN 50281-1-2 standards (EEx-d certification for explosion proof type of protection).

The matching of the head with the extension below the head and the cover (threaded) ensures a degree of protection from IP66 to IP68. The head also has a chain to connect the body to the cover, which facilitates the use of the instrument during the maintenance on systems. The single or double threaded electrical cable entry can be: M20x1.5, 1/2" NPT or 3/4" NPT, G1/2".


Fig. 4:Housing TA21H

Extension neck

A special extension is inserted between the husing and the thermowell connection, this part is called neck. The neck is constituted by a tube assembled to hydraulic hardware (nipples or joints) that is suitable to allow the adjustment of the sensor to the thermowell.

In addition to the standard versions listed below, it is also possible to order the extension neck by specifying the desired length (see "Sales structure" chart at the end of this document). In the TR63 the standard lengths (N) and the versions of the extension neck can be selected among the following options:

Тр	Material	N length	Thread	С	Neck
		mm		mm	dwg type
Ν	316	69	1/2" NPT M	8	А
Ν	316	109	1/2" NPT M	8	А
NU	316	84	1/2" NPT F	8	D
NUN	316	136	1/2" NPT M	8	F
Ν	A105	69	1/2" NPT M	8	А
Ν	A105	109	1/2" NPT M	8	А
NU	A105	104	1/2" NPT F	8	D
NUN	A105	148	1/2" NPT M	8	F



As illustrated by the drawing in fig. 5, the length of the extension neck may influence the temperature in the head. It is necessary that this temperature is kept within the limit values defined in the paragraph "Operating Conditions".

Before choosing the connection, it is better to verify this graphic and therefore to choose a suitable extension to avoid the heating of the head.

Fig. 5:Heating of the head caused by the process temperature

Electronic head transmitter

The required type of output signal can be obtained by choosing the correct head mounted transmitter. Endress+Hauser supplies "state-of-the-art" transmitters (the iTEMP® series) built in 2-wire technology and with 4...20 mA output signal, HART® or PROFIBUS-PA®. All of the transmitters can be easily programmed using a PC:

Head transmitter	Communication software
PCP TMT181	ReadWin® 2000
HART® TMT182	ReadWin® 2000, FieldCare, Hand held module DXR275, DXR375

Head transmitter	Communication software
PROFIBUS PA® TMT184	FieldCare


In the case of PROFIBUS-PA® transmitters, E+H recommends the use of PROFIBUS® dedicated connectors. The Weidmüller type is provided as a standard option. For detailed information about transmitters, please refer to the relevant documentation (refer to TI codes at the end of the document). If a head-mounted transmitter is not employed, the sensor probe may be connected through the terminal block to a remote converter (i.e. DIN rail transmitter). The customer may specify the configuration desired during the order phase. The head-mounted transmitters available are:

Description	Dwg
TMT180 and TMT181:PCP 420 mA. The TMT180 and the TMT181 are PC programmable transmitters. The TMT180 is also available in a version with enhanced accuracy (0.1°C vs. 0.2°C) in the temperature range – 50250°C and in a version with a fixed measurement range (specified by the customer in the order phase). The TMT182 output consists of 420 mA and HART® superimposed signals. TMT182: Smart HART®.	
TMT184: PROFIBUS-PA®. For the TMT184, with PROFIBUS-PA® output signal, the communication address may be set via software or via mechanical dip-switch.	

Thermowell

The thermowell is a component of the TR63 that must tolerate most of the mechanical stress transmitted by the process.

It is made from pipe and supplied in different materials and dimensions, according the chemical/physical characteristics of the process: corrosion, temperature, pressure and speed of the fluid.



The thermowell consists of three parts: • the extension neck (indicated as E), represents the external part of the thermowell and is connected with the head of the probe by means of a neck (usually a nipple) • the immersed part (identified as L), is situated next to the process connection in direct contact with the fluid process. • The welded threaded or flanged and the sliding complession fitting, are the process

connection that represents the part inserted between the extension and the immersed part and guarantees the mechanical and hydraulic sealing of the thermometer and plant.

The external finishing of the thermowell stem is available with a standard value of Ra $<1.6~\mu m$ (different finishes are available on request).

Fig. 6: Thermowell with threaded or flanged process connection

Warning:

The total standard length (A) of the thermowell must never exceed 3000 mm (that represents the standard length of pipe-bars; higher lengths are available only on request).

Process connection

		can b	e differei	nt: SS 316	/1.4401c	or ASTM A	A105/S	t 52.3 U	J standa	rd materi	al.	
		When	n it is ne	cessary to	have a fla	ange in sp	ecial m	aterial, 1	more re	sistant at	the corr	osion (example Hastelloy
		C276), it is ch	neaper to	choose ar	n economi	c versio	on comp	osed by	a flange	in SS316	6/1.4401 with on wetted
		part a	n platted	in Hastello	oy C276/	2.4819 (this sol	ution is	very les	s expensi	ve).	
Туре	Thread or Flange	Ø D1	Ø D2	Ø D3	Ø D4	D4 Nr	S1	S2	S 3	Α	A1	74
Flange	1" ANSI 150 RF	11	50,8	107,9	15,9	4	1,6	17,5	11	11	11	D1 WELDED
Flange	1" ANSI 300 RF	11	50,8	123,8	19,0	4	1,6	27,0	11	11	11	Threaded
Flange	1" ANSI 600 RF	11	50,8	123,8	19.0	4	6,4	11	27,0	11	11	Process
Flange	1" 1/2 ANSI 150 RF	11	73,0	127,0	15,9	4	1,6	22,2	11	11	11	
Flange	1" 1/2 ANSI 300 RF	11	73,0	155,6	22,2	4	1,6	30,2	11	11	11	WELDED
Flange	1" 1/2 ANSI 600 RF	11	73,0	155,6	22.2	4	6,4	11	31,7	11	11	
Flange	2" ANSI 300 RF	11	92,1	165.1	19,0	8	1,6	33,3	11	11	11	
Flange	2" ANSI 600 RF	11	92,1	165,1	19,0	8	6,4	11	36,5	11	11	
	1			1	1	1	1	1	1			► D1 Flanged Process
All the di	mension are in "mm"											SLIDING_
												SLIDING
T 1 1		21.2								10.0	0.1	Compression
Thread	1/2" NPT - M	21,3	11	//	11	//	11	11	//	19,9	8,1	Fitting Process
Thread	3/4" NPT - M	26,7	11	11	11	11	11	11	//	20,2	8,6	
Thread	1" NPT - M	33,4	11	11	11	11	11	//	//	25,0	10,1	
J	1	On re	emiest it	is possible	e to select	also diffe	rent ma	terials	finishing	s and co	nnection	\$
		01110	quest, it	10 000000		uibo uiiic	10110 1110			5 4114 00	meetion	.

Probe

In the TR63 the measuring probe are two:

• the TPR100 (for general purpose application)

• the TPR300 (ATEX certificated application)

Both of the probe are made in mineral insulated cable (MgO), with sheath in AISI316/1.4401.


The Immersion length (U) of the sensor can be chosen within a standard range from 50 to 3000 mm (see "Warning" in the "thermowell" section).

The standard process connections are threaded or flanged. When the process connection is threaded the material of connection is the same at the thermowell instead, when the process connection is flanged the material

The sensors with a Immersion length (U) > 3000 mm can be supplied after a technical verification of the specific applications from our technical office in the E+H Customer Service Department.

For replacement of the insert, it is necessary to refer the following table to have the IL (applicable only to standard thickness well bottoms). The immersion length of the insert spare part (IL) is calculated adding the total length of the thermowell (A = L + E) and the length of neck (N) used.

Insert general purpose	Ø,mm	N, tp.	N, mm	N, material	N, thread	IL, (mm)
TPR100	3 or 6	Ν	69	A105	1/2"NPT M	IL = L + E + 69 + 41
TPR100	3 or 6	Ν	109	A105	1/2"NPT M	IL = L + E + 109 + 41
TPR100	3 or 6	NU	96	A105	1/2"NPT F	IL = L + E + 96 + 41
TPR100	3 or 6	NUN	148	A105	1/2"NPT M	IL = L + E + 148 + 41
Insert ATEX certified	Ø,mm	N, tp.	N, mm	N, material	N, thread	IL, (mm)
TPR300	3 or 6	Ν	69	SS316	1/2"NPT M	IL = L + E + 69 + 41
TPR300	2 . () T	100			
1PR300	3 or 6	Ν	109	SS316	1/2"NPT M	IL = L + E + 109 + 41
TPR300	3 or 6	N NU	109 96	SS316 SS316	1/2"NPT M 1/2"NPT F	IL = L + E + 109 + 41 $IL = L + E + 96 + 41$






Fig. 7: Functional components, standard electrical diagrams (ceramic terminal block)

Certificates	&	approvals
--------------	---	-----------

Ex approval	 ATEX Certificate CESI 05ATEX038 for explosion proof type of protection: ATEX II 2 GD EEx-d IIC T6T5 T85°T100°C. The TR63 is C€ marked. ATEX Certificate KEMA 01ATEX1169 X for intrinsecaly safe type of protection: 1GD or 1/2 GD EEx-ia IIC T6T1 T85450°C. The TR63 is C€ marked. With regards to the NAMUR NE 24 certificate and the Manufacturer's Declaration according to the standard EN 50018, EN 50020, EN 50281-1-1, EN 50281-1-2, E+H Customer Service will be able to provide further detailed information.
PED approval	The Pressure Equipment Directive (97/23/CE) is respected. As paragraph 2.1 of article 1 is not applicable to these types of instruments. The C ϵ mark according to PED Directive is not requested.
Material certification	The material certificate EN 10204 3.1 can be directly selected from the sale structure of the product and refers to the parts of the sensor in contact with the process fluid. Other types of certificates related to materials can be requested separately. The "short form" certificate includes a simplified declaration with no enclosures of documents related to the materials used in the construction of the single sensor and guarantees the traceability of the materials through the identification number of the thermometer. The data related to the origin of the materials can subsequently be requested by the client if necessary.

Test on thermowellThe pressure tests are carried out at ambient temperature in order to verify the resistance of the thermowell to
the specifications indicated by the norm DIN 43772.
With regards to the thermowells that do not comply with this norm (with a reduced tip, a tapered tip on a 9

mm tube, special dimensions), the pressure of the corresponding straight tube with similar dimensions is verified. The sensors certified for use in Ex Zones, are always tested to pressure according to the same criterions.

Further details

Maintenance

The Omnigrad S TR63 thermometers do not require any specific maintenance. In the case of ATEX certified components (transmitter, insert or thermowell) please refer to the corresponding specific relevant documentation (at the end of the document).

Ordering information

Sales structure	TR63-	- Omnigrad S TR63. RTD thermometer Thermometer complete of DIN style pipe thermowell. Replaceable mineral insulated inset, spring loaded in terminal head, IP66 connection with epoxy coating. Two operating and measurement ranges: from -50 to 400°C (with TF); -200 to 600°C (with WW)							
		Approval: A Non-harzardous area							
		B		EX II 1 GD EEx ia IIC					
		C		EX II 1/2 GD EEX ia IIC					
		E *ATEX II 1/2 GD EEX d IIC M *ATEX II 1/2 GD EEX d IIC							
		Head, material, IP grade A TA21H Alu. epoxy coating, IP66							
			Y	Special version, to be specified					
			•						
				Cable entry					
				A 1 x 1/2 NPT					
				$\mathbf{B} = 2 \times 1/2 \text{ NPT}$					
				C 1 x 3/4 NPT					
				D 2 x 3/4 NPT					
				E 1 x M20 x1,5					
				F 2 x M20 x1,5					
				Y Special version, to be specified					
		Neck length N; Material; Fitting							
				A not needed					
				B 69 mm, SS 316, N, 1/2"NPT M					
				C 109 mm, SS 316, N, 1/2"NPT M					
				D 96 mm, SS 316, NU, 1/2"NPT F					
				E 136 mm, SS 316, NUN, 1/2"NPT M					
				F 69 mm, A105, N, 1/2"NPT M					
				G 109 mm, A 105, N, 1/2"NPT M					
				H 96 mm, A 105, NU, 1/2"NPT F					
				J 148 mm, A 105, NUN, 1/2"NPT M					
				Y Special version, to be specified					
				Thermowell material:					
				B 1/4" SCH.80, SS 316/1.4401					
				D 1/2" SCH.80, SS 316/1.4401					
				E 1/2" SCH.80, SS 446/2.xxxx					
				F 3/4" SCH.80, SS 316/1.4401					
				G 3/4" SCH.40, SS 446/2					
				H 3/4" SCH.40, I 600/2.4816					
				Y Special version, to be specified					

	Extension	on T; D1; Df; Q1; Q2					
		mm; 0 mm; 0 mm; flat ENI TUB 1					
		mm; 0 mm; 0 mm; round ENI TUB 2					
		120 mm; 65 mm; 014 mm; Welded MEU8					
		cial version, to be specified					
	Inc	ertion Length L:					
	X	mm					
	Y	Special version, to be specified					
	1 1*						
		Process connection:					
		AA not needed					
		11 thread 1/2" NPT - M 22 thread 3/4" NPT - M					
		33 thread 1" NPT - M					
		44 Compression fitting 1-1/2"NPT - M					
		CA 1" ANSI 150 RF BL, A105					
		CB 1" ANSI 150 RF BL, 316					
		CC 1" ANSI 300 RF BL, A105					
		CD 1" ANSI 300 RF BL, 316					
		CE 1" ANSI 600 RF BL, A105					
		CF 1" ANSI 600 RF BL, 316					
		CG 1"1/2 ANSI 150 RF BL, A105					
		CH 1" 1/2 ANSI 150 RF BL, 316					
		CJ 1" 1/2 ANSI 300 RF BL, A105					
		CK 1" 1/2 ANSI 300 RF BL, 316					
		CL 1" 1/2 ANSI 600 RF BL, A105					
		CM 1" 1/2 ANSI 600 RF BL, 316					
		CQ 2" ANSI 300 RF BL, A105					
		CS 2" ANSI 600 RF BL, A105 CT 2" ANSI 600 RF BL, 316					
		CT 2" ANSI 600 RF BL, 316 CV 2" ANSI 300 RF BL, 316					
		YY Special version, to be specified					
		Head transmitter; Range:					
		F Flying leads C Terminal block					
		2 TMT180-A21 fix; 0.2K, fromto°C, span limit -200/650°C					
		3 TMT180-A22 fix; 0.1K, from.to°C, span limit -50/250°C					
		4 TMT180-A11 prog.; 0.2K, fromto°C, span limit -200/650°C					
		5 TMT180-A12 prog.; 0.1K, fromto°C, span limit -50/250°C					
		P TMT181-A, PCP, fromto°C, 2-wire, isolated					
		Q TMT181-B, PCP ATEX, fromto°C, 2-wire, isolated					
		R TMT182-A, HART, fromto°C, 2-wire, isolated					
		TMT182-B, HART ATEX, fromto°C, 2-wire, isolated					
		S TMT184-A, Profibus PA, fromto°C, 2-wire, isolated					
		V TMT184-A, Profibus PA ATEX, fromto°C, 2-wire, isolated					
		1 THT1 separate item					
		RTD Class; Wiring					
		3 1 x Pt100 TF, cl. A, range: -50/400°C; 4-wire					
		7 1 x Pt100 TF, cl. 1/3 DIN B, range: -50/400°C; 4-wire					
		B 2 x Pt100 WW, cl. A, range: -200/600°C; 3-wire					
		C 1 x Pt100 WW, cl. A, range: -200/600°C; 4-wire					
		D 2 x Pt100 WW, cl. A, range: -200/600°C; 2-wire					
		F 2 x Pt100 WW, cl. 1/3 DIN B, range: -200/600°C; 3-wire					
		G 1 x Pt100 WW, cl. 1/3 DIN B, range: -200/600°C; 4-wire					
		Y Special version, to be specified					
		Additional options					
		0 Not needed					
		Y Special version, to be specified					
TR63-		← Order code (complete)					

Sales structure

THT1	Mode	and version of the head transmitter					
	A11	TMT180-A11 programmable fromto°C, accuracy 0.2 K, span limit -200650°C					
	A12	TMT180-A12 programmable fromto°C, accuracy 0.1 K, span limit -50250°C					
	A13	TMT180-A21AA fixed range, accuracy 0.2 K, span 050°C					
	A14	TMT180-A21AB fixed range, accuracy 0.2 K, span 0100°C					
	A15	TMT180-A21AC fixed range, accuracy 0.2 K, span 0150°C					
	A16	TMT180-A21AD fixed range, accuracy 0.2 K, span 0250°C					
	A17	TMT180-A22AA fixed range, accuracy 0.1 K, span 050°C					
	A18	TMT180-A22AB fixed range, accuracy 0.1 K, span 0100°C					
	A19	TMT180-A22AC fixed range, accuracy 0.1 K, span 0150°C					
	A20	TMT180-A22AD fixed range, accuracy 0.1 K, span 0250°C					
	A21	TMT180-A21 fixed range, accuracy 0.2 K, span limit -200650°C, fromto°C					
	A22	TMT180-A22 fixed range, accuracy 0.1 K, span limit -50250°C, fromto°C					
	F11	TMT181-A PCP, 2-wire, isolated, programmable fromto°C					
	F21	TMT181-B PCP ATEX, 2-wire, isolated, programmable fromto°C					
	F22	TMT181-C PCP FM IS, 2-wire, isolated, programmable fromto°C					
	F23	TMT181-D PCP CSA, 2-wire, isolated, programmable fromto°C					
	F24	TMT181-E PCP ATEX II3D, 2-wire, isolated, programmable fromto°C					
	F25	TMT181-F PCP ATEX II3D, 2-wire, isolated, programmable fromto°C					
	L11	TMT182-A HART®, 2-wire, isolated, programmable fromto°C					
	L21	TMT182-B HART® ATEX, 2-wire, isolated, programmable fromto°C					
	L22	TMT182-C HART® FM IS, 2-wire, isolated, programmable from to °C					
	L23	TMT182-D HART® CSA, 2-wire, isolated, programmable fromto°C					
	L24	TMT182-E HART® ATEX II3D, 2-wire, isolated, programmable fromto°C					
	L25	TMT182-F HART® ATEX II3D, 2-wire, isolated, programmable fromto°C					
	K11	TMT184-A PROFIBUS-PA®, 2-wire, programmable fromto°C					
	K21	TMT184-B PROFIBUS-PA® ATEX, 2-wire, programmable fromto°C					
	K22	TMT184-C PROFIBUS-PA® FM IS, 2-wire, programmable fromto°C					
	K23	TMT184-D PROFIBUS-PA® CSA, 2-wire, programmable fromto°C					
	K24	TMT184-E PROFIBUS-PA® CSA, 2-wire, programmable fromto°C					
	K25	TMT184-F PROFIBUS-PA® ATEX II3D, 2-wire, isolated, programmable fromto°C					
	YYY	Special transmitter					
		Application and services					
		1 Assembled into position					
		9 Special version					
THT1-		$\leftarrow \text{Order code (complete)}$					

Supplementary documentation

Brochure Field of activities - Temperature measurement	FA006T/09/en
Temperature head transmitter iTEMP® Pt TMT180	TI088R/09/en
Temperature head transmitter iTEMP® PCP TMT181	TI070R/09/en
Temperature head transmitter iTEMP® HART® TMT182	TI078R/09/en
Temperature head transmitter iTEMP® PA TMT184	TI079R/09/en
Safety instructions for use in hazardous areas (TPR100)	XA003T/02/z1
RTD insert for temperature sensors - Omniset TPR 100	TI268T/02/en
\square RTD insert for temperature sensors – Omniset TPR 300 to be released	TI290T/02/en
\Box Industrial thermometers, RTD and thermocouples	TI236T/02/en
\square Safety instructions for use in hazardous areas (TPR 300 to be released)	XA015T/02/z1

International Head Quarter

Endress+Hauser GmbH+Co.KG Instruments International Colmarer Str. 6 79576 Weil am Rhein Germany

Tel. +49 76 21 9 75 02 Fax +49 76 21 9 75 34 5 www.endress.com info@ii.endress.com

