Important Notice

NOITUAD

be present on the connection terminals or the probe itself. high voltage environment and a fault or installation error occurs, high voltage may Electrical shock could cause death or serious injury. If the sensor is installed in a

enclosed CD-ROM. read, understood and followed. For Endress+Hauser temperature transmitters see operating instructions of the used transmitters and all included safety notes are Safe and secure operation of the temperature sensor can only be guaranteed if the

esu rorrect use

instructions must be tollowed! unit. The installation conditions and connection values indicated in the operating The manufacturer cannot be held responsible for damage caused by misuse of the

NOITUAD 🚹

Maximum working pressure = $P_{atm.}$ (Atmospheric pressure) thermowell. It is not meant to be used directly in pressurized applications; The Thermocouple assembly ($T \leq 5$) is designed to be used in conjunction with a

Installation Guidelines and Safety instructions

1. Install the unit according to the relevant NEC Code and local regulations.

wrenches should be utilized. 2. Avoid any spark due to impact, friction and installation. Anti-sparking

instructions, see corresponding Control Drawing: 3. Approved apparatus must be installed in accordance with manufacturer's

XP NI DIP Class I, II, III Div. 1+2	ЕW	ZD063R/09/en
XP DIP Class I, II, III Div. 1+2	EW	ZD056R/09/en
XP NI DIP Class I, II, III Div. 1+2	CSA	ZD054R/09/en
XP DIP Class I, II, III Div. 1+2	CSA	ZD052R/09/en
IgvorgA		Drawing code

Endress+Hauser 4 소 Poople for Process Automatic



tions. The sensor is designed to ensure highest accuracy and long term stability.

sure for process industry. thermocouple as a measurement probe.

The sensor is made up of a MgO insulated The thermocouple sensor complies with the ASTM E-230 and IEC60584 specifica-

Thermocouple Assembly T55

Measuring System

Explosion proof Thermocouple assembly T55 with spring loaded insert and enclo-

Compact Instructions

Explosion proof

71208024

Installation and operation

connection schematics. Procedures indicated in these instructions must be must make sure that the measurement system has been correctly wired to the personnel who are authorized to do so by the plant operator. The plant operator wiring and maintenance of the unit must only be completed by trained, skilled installed incorrectly or misused, certain application dangers can occur. Installation, complies with the safety requirements of the local guidelines. However, if it is The unit is constructed using the most up to date production equipment and

For further information regarding connections, please refer to the corresponding

are not supplied with the sensors. These are the customer's responsibility. The accessories for pipe connections and the appropriate gaskets and sealing rings

.b9wollot

Standards.

Please follow the Return Authorization Policy which is attached with this manual. sumpar

Safety pictograms and symbols

Ч

Notes draw attention to activities or procedures that can have a direct influence

on operation or trigger an untoreseen device reaction if they are not carried out

properly.

NOITUAD

carried out properly. seriously injured, to safety risks or to the destruction of the device if they are not Cautions draw attention to activities or procedures that can lead to persons being

socilications without notice. patent. Please note that Endress+Hauser reserves the right to change and/or improve the product design and to the products; and recommendation for the use of the product/process information in conflict with any angrantee' expressed or implied, regarding performance; merchantability, fitness, or other matter with respect herein is NOT a guarantee of satisfactory results. Specifically, this information is neither a warranty nor Though the information provided herein is believed to be accurate, be advised that the information contained



www.addresses.endress.com

Supplementary documentation and field transmitters are available on CD-ROM, find enclosed or order by order number: SONDTT-AG.

All important Temperature Operating Instructions, particularly with regard to head

non-current-carrying metal parts (e.g. insert sheath)

The units are factory tested with 850 V_{DC} for one second Dielectrical strength between live parts (leads/terminals) and exposed


* For measurement errors in °F, calculate using equation above in °C, then multiply the outcome by 1.8.


J	0 to 760	32 to 1400	\pm 1.1 or \pm 0.4%	\pm 2.2 or \pm 0.75%
K	0 to 1260	32 to 2300	\pm 1.1 or \pm 0.4%	± 2.2 or ± 0.75%
Т	0 to 370	32 to 700	$\pm~0.5~\text{or}\pm~0.4\%$	± 1 or ± 0.75%
N	0 to 1260	32 to 2300	$\pm \ 1.1 \ \text{or} \pm 0.4\%$	$\pm 2.2 \text{ or } \pm 0.4\%$
			-	

Performance Characteristics Maximum measured error

Type

Е








Installation

Installation locations



Examples of spring loaded insert installation.

- A: Explosion proof Thermocouple assembly T55 installed within a socket weld thermowell
 B: Explosion proof Thermocouple assembly T55 installed within a tilted installed threaded thermowell
- C: Explosion proof Thermocouple assembly T55 installed within a flanged thermowell

For installation proceed as follows:


1. Seal the extension nipples with TFE tape before screwing in the device.

2. Screw the explosion proof Thermocouple assembly T55 only into an already prepared thermowell.

Do not install the Explosion proof Thermocouple assembly T55 directly to the process pipe or process container wall. Otherwise it could cause death or serious injury!

Dimensions

with spring loaded insert and flamepath nipple: All dimensions in inches.



E = Extension length

LN = Lamination nipple (flamepath nipple)

 X_{A1} = Insert immersion length


 X_{A2}^{A1} = Spring loaded insert immersion length TU221 as spare part with lamination nipple

For spare part spring loaded insert, TU221, please contact Endress+Hauser!

X _{A1}	E (nom. dimension)
4", 6", 9", 12"; specified length 4" to 100" in ½" increments	Lamination Nipple Union Nipple
X _{A2}	(LUN) 3" or 6"
Calculate as follows: $X_{A2} = X_{A1} + E$	5 01 0

Electrical connection-wiring diagrams

Head mounted transmitter (single/dual) Field mounted transmitter



Wire specifications: Thermocouple grade, TFE insulated 20AWG, 7 strands with stripped ends

Flying leads, standard 3" for wiring in terminal head, head transmitter or terminal block	
mounted	

Flying leads, $5\%^{\prime\prime}$ for wiring with field housing or field transmitter assembly

The blocks and transmitters are shown as they will sit inside the heads in reference to the conduit opening. ALWAYS terminate leads to the outside screw!

Recommended minimum immersion:

2.5 inches for the 1/4" OD thermocouple sheath, nominal

Technical data

Upper temperature limits for various thermocouple types in °F (°C)					
Sheath OD	Туре Т	Туре Ј	Туре Е	Туре К	Type N
ؼ"	700 °F (370 °C)	1330 ℉ (720 ℃)	1510 °F (820 °C)	2100 °F (1	150 °C)

Thermocouple color codes as per ASTM E-230

Weight		From 1 to 5.5 lbs
Material	Max. temp. rating	Application notes
316SS	1700 °F (927 °C)	Superior corrosion resistance. Duplex version of type N is not available with 316SS sheats.
Inconel 600	2100 ℉ (1149 ℃) ¹	Excellent oxidation and corrosion resistance at high tem- perature. Not to be used in sulphurous atmospheres over 1000 °F (538 °C). Types T & J are not available with Inconel 600 sheats.

1) Max. working temperature under oxidizing conditions: reducing conditions reduce max. temp. to 1900 °F (1038 °C).

Shock and vibration resistance

4g/2 to 150 Hz as per IEC 60 068-2-6

Ambient temperature limits*

Housing without head-mounted transmitter			
Aluminium pressure die-cast housing	-58 to 212 °F (-50 to 100 °C)		
Stainless steel housing	-58 to 212 °F (-50 to 100 °C)		
Housing with head-mounted transmitter			
All types of housing	-40 to 185 °F (-40 to 85 °C)		
Field transmitter			
with display	-40 to 158 °F (-40 to 70 °C)		
without display	-40 to 185 °F (-40 to 85 °C)		

*For hazardous areas refer to the transmitter control drawing