



Industrial protecting tube *omnigrad TA555*

Heavy duty - General purpose
From round bar stock - Ø 34 mm
1" NPT threaded or flanged weld type
Also ME U 819.04 - type 6



Threaded
process connection



Flanged
process connection

Description

TA555 is an industry standard thermowell, manufactured from round bar stock (drilled).

The process connection can be threaded or flanged weld.

The thermowell stem shape can be straight or conical.

The extension and the immersion lengths as well as the bar dimensions can be chosen according to process requirements.

A wide choice of standard materials and process connections is available; other versions can be ordered according to specification.

Different grades of surface finishing are also available.

Application

TA555 is designed for use with resistance and thermocouple thermometers mainly in heavy duty applications.

Technical data

Round bar	Standard reference:	ME U 819.04 - type 6
	Extension O.D.:	34 mm
	Immersion O.D.:	≤ 28 mm
	Standard ext. length:	75 mm
	Standard bore diameter:	6.5, 7 or 8 mm
	Standard material:	AISI316/W.1.4401, AISI316L/W.1.4404

Connection to thermometer	Threaded:	1/2" NPT - female
----------------------------------	-----------	-------------------

Process connection	Type:	threaded or flanged weld
	Thread:	1" NPT
	Flange type:	ANSI slip-on
	Flange material:	AISI 316 or A 105
	Flange mounting:	threaded and back welded - 3x3 mm wide

Tip	Bottom shape:	straight or conical
	Std. bottom thickness:	5 mm

Surface	Finishing:	refer to the order key
----------------	------------	------------------------

**Supplementary
Documentation**

- Technical Information Industrial Protecting Tubes (TI138T/02/en)

Endress+Hauser
GmbH+Co.
Instruments International
P.O. Box 2222
D-79574 Weil am Rhein
Germany

Tel. (07621) 975-02
Tx 773926
Fax (07621) 975 345
<http://www.endress.com>
info@ii.endress.com

Endress + Hauser
The Power of Know How

