## Important Notice

## NOITUAD A

be present on the connection terminals or the probe itself. high voltage environment and a fault or installation error occurs, high voltage may Electrical shock could cause death or serious injury. If the sensor is installed in a

enclosed CD-ROM. read, understood and followed. For Endress+Hauser temperature transmitters see operating instructions of the used transmitters and all included safety notes are Safe and secure operation of the temperature sensor can only be guaranteed if the

## Sorrect use

instructions must be followed! unit. The installation conditions and connection values indicated in the operating The manufacturer cannot be held responsible for damage caused by misuse of the

## Installation Guidelines and Safety instructions

1. Install the unit according to the relevant NEC Code and local regulations.

Z. Avoid any spark due to impact, friction and installation. Anti-sparking

3. Approved apparatus must be installed in accordance with manufacturer's wrenches should be utilized.

instructions, see corresponding Control Drawing:

ZD062R/09/en	ЕW	XP NI DIP Class I, II, III Div. 1+2
ZD057R/09/en	ЕW	XP DIP Class I, II, III Div. 1+2
ZD055R/09/en	CSA	XP NI DIP Class I, II, III Div. 1+2
ZD053R/09/en	CSA	XP DIP Class I, II, III Div. 1+2
Drawing code		IsvorqqA

For further information regarding connections, please refer to the corresponding sealing and the applicable torques must be selected by the user. Depending on temperature and pressure operating conditions, the gaskets, the are not supplied with the sensors. These are the customer's responsibility. The accessories for pipe connections and the appropriate gaskets and sealing rings

Standards.

KA00244R/24/AE/13.12

71208022

# **Measuring System**

Explosion proof Thermocouple assembly provided with flanged thermowell and enclosure for process industry. The sensor is made up of a MgO insulated thermocouple as a measurement probe and a thermowell made of bar-stock material.

The thermocouple sensor complies with the ASTM E-230 and IEC60584 specifications. The sensor is designed to ensure

highest accuracy and long term stability.

# Assembly in flanged Thermowell T54

# **Compact Instructions Explosion proof Thermocouple**

## Maximum measured error Temperature range Standard Tolerance in % and $^\circ\!C^*$ (whichever is greater) Туре °C IEC class 1 IEC class 2 °F 32 to 1600 ± 1 or ± 0.4% E 0 to 870 ± 1.7 or ± 0.5% 0 to 760 ± 2.2 or ± 0.75% 32 to 1400 ± 1.1 or ± 0.4% К 0 to 1260 32 to 2300 $\pm~1.1~\mathrm{or}\pm0.4\%$ ± 2.2 or ± 0.75% Т

Dielectrical strength

The units are factory tested with 850  $V_{DC}$  for one second between live parts (leads/terminals) and exposed

Ν	0 to 1260	32 to 2300	$\pm \ 1.1 \ \text{or} \pm 0.4\%$	± 2.2 or ± 0.4%
* For mea	surement errors ir	1 °F, calculate usir	ng equation above in °C, th	en multiply the outcome by 1.

IN	0 to 1260	32 to 2300	$\pm 1.1 \text{ or } \pm 0.4\%$	$\pm$ 2.2 or $\pm$ 0.4%
* For mea	asurement errors ir	n°E calculate usir	ng equation above in °C th	en multiply the outcome by 1.8

	0101260	3Z LO Z3UU	$\pm 1.1$ or $\pm 0.4\%$	± 2.2 0f ± 0.4%
or mea	surement errors in	ı °F, calculate usir	ng equation above in °C, th	en multiply the outcome by 1.8.

	0 to 1260	32 to 2300	$\pm 1.1 \text{ or } \pm 0.4\%$	± 2.2 or ± 0.4%
mea	surement errors in	ı °F, calculate usir	ng equation above in °C, th	en multiply the outcome by 1.8

All important Temperature Operating Instructions, particularly with regard to head

and field transmitters are available on CD-ROM, find enclosed or order by order

* For mea	surement errors in	n °F, calculate usir	ng equation above in °C, th	nen multiply the outcome by 1.

0 to 370	32 to 700	± 0.5 or ± 0.4%	± 1 or ± 0.75%	
0 to 1260	32 to 2300	± 1.1 or ± 0.4%	± 2.2 or ± 0.4%	
 accurate a more in $^{\circ}$ calculate using equation shows in $^{\circ}$ C then multiply the outcome by 1.9				

non-current-carrying metal parts (e.g. insert sheath)

4q/2 to 150 Hz as per IEC 60 068-2-6



Installation and operation

Satety pictograms and symbols

ŗ

sumay

followed.

properly. on operation or trigger an untoreseen device reaction if they are not carried out Notes draw attention to activities or procedures that can have a direct influence

Please follow the Return Authorization Policy which is attached with this manual.

connection schematics. Procedures indicated in these instructions must be

must make sure that the measurement system has been correctly wired to the personnel who are authorized to do so by the plant operator. The plant operator

wiring and maintenance of the unit must only be completed by trained, skilled

complies with the safety requirements of the local guidelines. However, if it is

The unit is constructed using the most up to date production equipment and

installed incorrectly or misused, certain application dangers can occur. Installation,

**NOITUAD** 

carried out properly. seriously injured, to safety risks or to the destruction of the device if they are not Cautions draw attention to activities or procedures that can lead to persons being

Though the information provided herein is believed to be accurate, be advised that the information contained

specifications without notice.

patent. Please note that Endress+Hauser reserves the right to change and/or improve the product design and to the products; and recommendation for the use of the product/process information in conflict with any guarantee, expressed or implied, regarding performance; merchantability, fitness, or other matter with respect herein is NOT a guarantee of satisfactory results. Specifically, this information is neither a warranty nor

Endress+Hauser

People for Process Automation

People for Process Automati



**Performance Characteristics** 

Supplementary documentation

www.addresses.endress.com


number: SONDTT-AG.

Solutions



## Installation

Installation locations



Examples of installation. In pipes of a small section the axis line of the duct must be reached and if possible slightly exceeded by the tip of the probe (=U).

- A: Pipe installation
- B: Container installation

For installation proceed as follows:


1. Attach thermowell to pipe or process container wall.

- Install and tighten the Thermowell before applying process pressure. 2. Make sure that the process fitting matches the maximum specified process pressure.
- 3. Seal the extension nipples with TFE tape before screwing the sensor into the thermowell.
- 4. Thermowells are used in measuring the temperature of a moving fluid in a conduit, where the stream exerts an appreciable force. The limiting value for the thermowells is governed by the temperature, the pressure and the speed of the medium, the immersion length, the materials of the thermowell and the medium, etc.

For operating conditions, a stress calculation should be carried out.

# Dimensions

With spring loaded insert and self contained nipple. All dimensions in inches.



Recommended minimum immersion for thermowell:


Tapered TW = 41/2"

Spare part insert, TU121. For replacement with additional option code (XP spare part) need to be used to assure approved classification, please contact Endress+Hauser!

3/4" straight TW = 4"

## Electrical connection-wiring diagrams

Head mounted transmitter (single/dual) Field mounted transmitter



Wire specifications: Thermocouple grade, TFE insulated 20AWG, 7 strands with stripped ends

Flying leads, standard 3" for wiring in terminal head, head transmitter or terminal block mounted

Flying leads, 5½" for wiring with field housing or field transmitter assembly



The blocks and transmitters are shown as they will sit inside the heads in reference to the conduit opening. ALWAYS terminate leads to the outside screw!

Flange rating: ASME B16.5					
U	E (nom. dimension)	Т	Flange size	ØQ	
16", 22";	Hex nipple = 1" or Nipple Union Nipple	specified length 1" to 10" in ½"	1" 1½"	7/8" 1 <sup>1</sup> /16"	
specified length 2" to 18" in ½" increments	(NUN) = 4" or 7" Mate- rial: Steel or 316SS	increments	2"	1 <sup>1</sup> /16"	

## Technical data

Upper temperature limits for various thermocouple types in $\ensuremath{^\circ} F$ ( $\ensuremath{^\circ} C$ )					
Sheath OD Type T Type J Type E Type K Type N					
ؼ"	700 °F (370 °C)	1330 °F (720 °C)	1510 °F (820 °C)	2100 °F (11	150 °C)

Thermocouple color codes as per ASTM E-230

## Ambient temperature limits\*

Housing without head-mounted transmitter		
Aluminium pressure die-cast housing -58 to 212 °F (-50 to 100 °C)		
Stainless steel housing -58 to 212 °F (-50 to 100 °C)		
Housing with head-mounted transmitter		
All types of housing -40 to 185 °F (-40 to 85 °C)		
Field transmitter		
with display	-40 to 158 °F (-40 to 70 °C)	
without display	-40 to 185 °F (-40 to 85 °C)	

\*For hazardous areas refer to the transmitter control drawing

Weight		From 1 to 10 lbs
Material	Max. temp. rating	Application notes
316SS	1700 °F (927 °C)	Superior corrosion resistance. Duplex version of type N is not available with 316SS sheats.
Inconel 600	2100 °F (1149 °C) <sup>1</sup>	Excellent oxidation and corrosion resistance at high tem- perature. Not to be used in sulphurous atmospheres over 1000 °F (538 °C). Types T & J are not available with Inconel 600 sheats.

1) Max. working temperature under oxidizing conditions: reducing conditions reduce max. temp. to 1900  $^\circ \! F$  (1038  $^\circ \! C).$