



















## **Technical Information**

# prosonic T FMU230, FMU231

Ultrasonic Level Measurement Compact transmitters for non-contact level measurement of fluids and coarse bulk materials



The compact transmitters Prosonic T are used for continuous, non-contact level measurement in fluids and coarse bulk and lumpy materials (grain size from 4 mm onwards).

The maximum measuring range is

- FMU 230:
  - 4m in fluids
  - 2m in bulk materials
- FMU 231:
  - -7m in fluids
  - 3,5 m in bulk materials

#### Your benefits

- Non-contact measurement method, therefore almost independent of product properties
- Integrated temperature sensor for time-of-flight correction. Accurate measurements, even for temperature changes
- Linearisation function for measured value output in
- with optional display
- simple mounting via G1½", G2", NPT 1½" or NPT 2"
- Two-wire instrument; level indicated by 4-20 mA output current




# **Table of Contents**

Function and system design
Time-of-flight method
Signal evaluation
Calibration
Linearisation
Input
Measured variable
Measuring range
Operating frequency
Operating nequency
Outsut
Output5
Output signal
Signal on alarm5
Output damping
Load
Auxiliary energy6
Electrical connection
Supply voltage
Power consumption
Cable entry
Performance characteristics6
Reference operating conditions
Measured value resolution
Measuring error
Pulse frequency
Reaction time
T . 44 .4
Installation conditions
Installation variants
Blocking distance,
nozzle mounting
Installation position
Ambient conditions
Ambient temperature8
Storage temperature
Climate class
Ingress protection
Vibration resistance
Electromagnetic compatibility (EMC)
2100201114griotic companies (21116)
Draces conditions
Process conditions9
Process temperature
Process pressure9
Mechanical construction
Design / Dimensions
Weight9
Housing material9
Process connection

Human interface	10
Operating elements	. 10
ĒD	. 10
Pisplay module	
optional)	. 10
Certificates and Approvals	1(
CE mark	. 10
external standards and guidelines	
Ordering information	1
roduct structure	. 1
cope of delivery	
Accessories	1
rotective cover	. 1
Adapter flange	
Mounting bracket	
Cantilever	
Nounting bracket	
Vall bracket for cantilever	
Supplementary documentation	1.
ystem–Information	
Information	

# Function and system design

### Time-of-flight method



E: Empty distance; F: Span (full distance); D: Distance from sensor membrane - product surface; L: Level; BD: Blocking distance

The sensor of the Prosonic T transmits ultrasonic pulses in the direction of the product surface. There, they are reflected back and received by the sensor. The Prosonic T measures the time t between pulse transmission and reception. The instrument uses the time t (and the velocity of sound c) to calculate the distance D between the sensor membrane and the product surface:

 $D = c \cdot t/2$ 

As the device knows the empty distance E from a user entry, it can calculate the level as follows:

L = E - D

An integrated temperature sensor compensates for changes in the velocity of sound caused by temperature changes.

### Signal evaluation

- Automatic suppression of up to 3 interference echoes (fixed target echoes)
- First echo detection

### Calibration

Calibration is performed by entering the empty distance E (=zero) and the full distance F (= span).

E and F correspond to

- 4 mA or 20 mA respectively for the current output
- 0% or 100% respectively for the local display

Span F may not extend into the blocking distance BD. Level echos from the blocking distance cannot be evaluated due to the transient characteristics of the sensor and a wrong measured value may result.

For the version with on-site display, E and F can be entered directly as numbers. For the version without display, calibration can be performed for example by filling the vessel to the E and F point consecutively.

### Linearisation

The linearisation function of the Prosonic T allows conversion of the measured value into any unit of length or volume. A linearisation table consisting of up to 11 value pairs can be entered manually or semi-automatically (by filling the vessel under controlled conditions).

# Input

#### Measured variable

The distance D between the sensor membrane and the product surface is measured .

Using the linearisation function, the device uses  $\ensuremath{\mathsf{D}}$  to calculate:

- level L in any units
- volume V in any units

### Measuring range

### Upper limit: blocking distance

Instrument	blocking distance (BD)
FMU 230	0,25 m
FMU 231	0,4 m

The upper limit of the measuring distance is given by the blocking distance (page 2). Level echos within the blocking distance cannot be evaluated due to the transient characteristics of the sensor.

### Lower limit: Range of the sensor

The measuring range is limited by the range of a sensor. The sensor range is, in turn, dependent on the operating conditions. To estimate the actual range, proceed as follows (see also the calculation example in the diagram):

- 1. Determine which of the influences shown in the following table are appropriate for your process.
- 2. Add the corresponding attenuation values.
- 3. From the total attenuation, use the diagram to calculate the range.

Fluid surface	Attenuation
Calm	0 dB
Waves	5 10 dB
Strong turbulence	10 20 dB
Foaming	Ask E+H


Bulk material surface	Attenuation
Hard, rough (e.g. rubble)	40 dB
Soft (e.g. peat, dust-covered clinker)	40 60 dB

Dust	Attenuation
No dust formation	0 dB
Little dust formation	5 dB
Heavy dust formation	5 20 dB

Filling curtain in detection range	Attenuation
None	0 dB
Small quantities	5 10 dB
Large quantities	10 40 dB

Temperature difference between sensor and product surface	Attenuation
to 20 °C	0 dB

Temperature difference between sensor and product surface	Attenuation
to 40 °C	5 10 dB
to 80 °C	10 20 dB



## Operating frequency


Instrument	Operating frequency
FMU 230	approx. 70 kHz
FMU 231	approx. 50 kHz

# Output

Output signal	4 20 mA analog signal
Signal on alarm	configurable:  3,8 mA 22 mA hold last value
Output damping	0 255s

5


Load



The maximum load  $(R_{\text{max}})$  depends on the supply voltage (U).

# Auxiliary energy

### **Electrical connection**



Use screened two-core instrumentation cable.For optimal protection against electromagnetic interference, the screen should be grounded in the control room or the nearest earthing point. A good connection to ground is essential to good screening.

Supply voltage	12 36 V <sub>DC</sub>
Power consumption	< 0,8 W
Cable entry	■ Cable gland M20x1,5 ■ Cable entry G ½ or ½ NPT cable diameter 5 9mm

# Performance characteristics


approx. 5 s

Reference operating conditions	The specified performance characteristics are valid under the following reference conditions:  Temperature = +20 °C  Pressure = 1013 mbar abs.  Humidity = 60 %  Ideal reflective surface (e.g. calm, smooth fluid surface)  No interference reflections within signal beam
Measured value resolution	3 mm
Measuring error	0,25% of maximum measuring range (includes linearity, repeatability, and hysteresis)
Pulse frequency	0,5 1 Hz

Reaction time

## Installation conditions


#### Installation variants



L00-FMUx3xxx-11-00-00-en-006

# Blocking distance, nozzle mounting

Level echos from the blocking distance (BD) cannot be evaluated due to the transient characteristics of the sensor. Install the Prosonic T at a height so that the blocking distance BD is not undershot, even at maximum fill level. Use a pipe nozzle if you cannot maintain the blocking distance in any other way. The interior of the nozzle must be smooth and may not contain any edges or welded joints. In particular, there should be no burr on the inside of the tank side nozzle end. Note the specified limits for nozzle diameter and length.




L00-FMUx3xxx-11-00-00-de-00

( ,

#### Caution.

If the blocking distance is undershot, it may cause device malfunction.

### Installation position



- L00-FMU23xxx-17-00-00-de-001
- Do not install the sensor in the middle of the tank (3). We recommend leaving a distance between the sensor and the tank wall (1) measuring 1/3 of the tank radius.
- Use a protective cover, in order to protect the device from direct sun or rain (2).
- Avoid measurements through the filling curtain (4).
- Make sure that equipment (5) such as limit switches, temperature sensors, etc. are not located within the emitting angle  $\alpha$ . In particular, symmetrical equipment (6) such as heating coils, baffles etc. can influence measurement.
- Align the sensor so that it is vertical to the product surface.
- Never install two identical ultrasonic measuring devices in a tank.
- To estimate the transmitted echo beam and its detection range, use the 3 dB emitting angle  $\alpha$ :

Sensor	α	L	r
FMU 230	11°	4 m	0,38 m
FMU 231	11°	7 m	0,67 m

# **Ambient conditions**


Ambient temperature	-20 °C +60 °C
Storage temperature	-40°C +80°C
Climate class	DIN/IEC 68 T2-30Db
Ingress protection	<ul> <li>with closed housing: IP 67, NEMA 6</li> <li>with open housing: IP 20, NEMA 1</li> <li>Sensor: IP 68</li> </ul>
Vibration resistance	DIN IEC 68 T2-6 Tab. 2C (10 55 Hz)
Electromagnetic compatibility (EMC)	<ul> <li>Interference emmission to EN 61326, Equipment class B</li> <li>Interference immunity to EN 61326, Appendix A (Industrial) und NAMUR reccomendation NE 21 (EMC)</li> </ul>

# **Process conditions**

Process temperature	-40°C +80°C	
Process pressure	0.7 3 har ahs	

# Mechanical construction

### Design / Dimensions



Weight

Instrument	Weight
FMU 230	approx. 1,5 kg
FMU 231	approx. 1,6 kg

Housing material


PBT glass reinforced / flame-retended

### **Process connection**

Instrument	Process connection	seal and sensor material
FMU 230	<ul> <li>thread G 1½"</li> <li>thread NPT 1½" - 11,5</li> </ul>	PVDF / EPDM
FMU 231	<ul><li>thread 2"</li><li>thread NPT 2" - 11,5</li></ul>	PVDF / EPDM

## Human interface

### Operating elements



**LED** 

Pressing of a key is confirmed by a flash of the green LED.

# Display module (optional)

When the display module is used, the Prosonic T is operated via an operating matrix. The current matrix position and the associated parameter (e.g. measured value) are displayed on the module. The bargraph represents the measured value or the echo quality, depending on the matrix position.

The basic functions for simple applications (empty and full calibration, locking and unlocking) are accesible without the display module.

# Certificates and Approvals

### CE mark

The measuring system meets the legal requirements of the EC-guidelines. Endress+Hauser confirms the instrument passing the required tests by attaching the CE-mark.

# External standards and guidelines

### EN 60529

Protection class of housing (IP-code)

#### EN 61326

Electromagnetic compatibility (EMC requirements)

### NAMUR

Standards committee for measurement and control in the chemical industry

# Ordering information

### **Product structure**


	Version									
	Е	Eur	ope	e / Asia (cylindrical thread "G")						
	A	Am	America (conical thread "NPT")							
			Ce	rtifi	cate					
			Α	Sta	ndar	d				
			N	CS.	A Ge	neral Purpose (for Version A only)				
				Co	mm	unication				
				Α	4	20mA, 2-wire				
					Housing/cable entry					
					2 Plastic housing NEMA 6, NPT ½					
					3 Plastic housing IP 67, M 20x1,5 (for Version E only)					
					4 Plastic housing IP 67, G ½ (for Version E only)					
						Display				
					1 without display module					
					2 with display module					
FMU 230		-			product designation					
FMU 231		-				product designation				

## Scope of delivery

- Instrument in the ordered version
- Operating Instructions
   for versions FMU 230E and FMU 231E: Counter nut (PC)
- EPDM process seal
- for versions M20x1,5: cable gland


# Accessories

### Protective cover



Order-Code: 942665-0000

### Adapter flange




Version with metrical thread (FAU 70 E)

	-	_						
	Pro	ocess Connection						
	12	DN 50 PN 16 A, flange EN1092-1 (DIN2527 B)						
	14	DN 80 PN 16 A, flange EN1092-1 (DIN2527 B)						
	15	DN 100 PN 16, A, flange EN1092-1 (DIN2527 B)						
		Senso	or Connection					
		3 Ti	hread ISO228 G1-1/2					
		4 Ti	hread ISO228 G2					
		FI	lange Material					
		2	316L					
		7	Polypropylene					
FAU 70 E			Product designation					

### Version with conical thread(FAU 70 A)

lbs FF, flange ANSI B16.5 lbs FF, flange ANSI B16.5 r Connection read NPT1-1/2
lbs FF, flange ANSI B16.5 r Connection
r Connection
read NPT1-1/2
read NPT2
ange Material
316L
Polypropylene
Product designation


### Mounting bracket



- for FMU 230, G1½: Order code: 942669-0000
- for FMU 231, G2: Order code: 942669-0001
- Material: 316 Ti
- lacksquare suited for NPT 1½" und 2" as well

12


## Cantilever



A	В	С	D	for Sensor	Material	Order Code
585 mm	250 mm	2 mm	200 mm	FMU 230	1.4301 (AISI 304)	52014132
					galv. steel	52014131
				FMU 231	1.4301 (AISI 304)	52014136
					galv. steel	52014135
1085 mm	750 mm	3 mm	300 mm	FMU 230	1.4301 (AISI 304)	52014134
					galv. steel	52014133
				FMU 231	1.4301 (AISI 304)	52014138
					galv. steel	52014137

The 50 mm or 62 mm orifices serve for the mounting of the FMU 230 or FMU 231 sensor, respecitvely.


# Mounting bracket



L00-FMU4x-00-00-00-yy-005

Height	Material	Order Code
700 mm	galv. steel	919791-0000
700 mm	316 Ti	919791-0001
1400 mm	galv. steel	919791-0002
1400 mm	316 Ti	919791-0003

### Wall bracket for cantilever



L00-FMU4x-00-00-00-yy-006

Material	Order Code
galv. steel	919792-0000
316 Ti	919792-0001

Supplementary do	ocumentation
------------------	--------------

System-Information	SI 005F
	Ultrasonic level measurement
Operating manual	KA 042F

### Instruments International

Endress+Hauser Instruments International AG Kaegenstrasse 2 4153 Reinach Switzerland

Tel. +41 61 715 81 00 Fax +41 61 715 25 00 www.endress.com info@ii.endress.com



People for Process Automation