

# Safety Instructions

## Liquiphant FTL64

4-20 mA HART

II 1/2 G Ex db ia IIC T6...T1 Ga/Gb

II 2 G Ex db ia IIC T6...T1 Gb

**UK  
CA**





# Liquiphant FTL64

4-20 mA HART

## Table of contents

Associated documentation .....	4
Supplementary documentation .....	4
Manufacturer's certificates .....	4
Manufacturer address .....	4
Other standards .....	4
Extended order code .....	5
Safety instructions: General .....	8
Safety instructions: Special conditions .....	8
Safety instructions: Installation .....	9
Safety instructions: Zone 0 .....	10
Safety instructions: Zone separation Zone 0, Zone 1 .....	11
Explosion protection with heat insulation .....	11
Temperature tables .....	12
Connection data .....	13

<b>Associated documentation</b>	<p>This document is an integral part of the following Operating Instructions: BA02215F</p>
<b>Supplementary documentation</b>	<p>Explosion protection brochure: CP00021Z The Explosion-protection brochure is available:</p> <ul style="list-style-type: none"><li>▪ In the download area of the Endress+Hauser website: <a href="http://www.endress.com">www.endress.com</a> -&gt; Downloads -&gt; Brochures and Catalogs -&gt; Text Search: CP00021Z</li><li>▪ On the CD for devices with CD-based documentation</li></ul>
<b>Manufacturer's certificates</b>	<p><b>UK Declaration of Conformity</b></p> <p>Declaration Number: UK_00529</p> <p>The UK Declaration of Conformity is available: In the download area of the Endress+Hauser website: <a href="http://www.endress.com">www.endress.com</a> -&gt; Downloads -&gt; Declaration -&gt; Type: UKCA Declaration -&gt; Product Code: ...</p> <p><b>UKCA type-examination certificate</b></p> <p>Certificate number: CML 22UKEX1611X</p> <p>List of applied standards: See UK Declaration of Conformity.</p>
<b>Manufacturer address</b>	<p>Endress+Hauser SE+Co. KG Hauptstraße 1 79689 Maulburg, Germany Address of the manufacturing plant: See nameplate.</p>
<b>Other standards</b>	<p>Among other things, the following standards shall be observed in their current version for proper installation:</p> <ul style="list-style-type: none"><li>▪ IEC/EN 60079-14: "Explosive atmospheres - Part 14: Electrical installations design, selection and erection"</li><li>▪ EN 1127-1: "Explosive atmospheres - Explosion prevention and protection - Part 1: Basic concepts and methodology"</li></ul>

## Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

### Structure of the extended order code

FTL64	–	*****	+	A*B*C*D*E*F*G*..
<i>(Device type)</i>		<i>(Basic specifications)</i>		<i>(Optional specifications)</i>

\* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

#### *Basic specifications*

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available.

The selected option of a feature can consist of several positions.

#### *Optional specifications*

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

### Extended order code: Liquiphant



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

#### *Device type*

FTL64

*Basic specifications*

Position 1, 2 (Approval)		
Selected option	Description	
FTL64	UB	UK Ex II 1/2 G Ex db ia IIC T6...T1 Ga/Gb UK Ex II 2 G Ex db ia IIC T6...T1 Gb

Position 3, 4 (Output)		
Selected option	Description	
FTL64	BA	FEL60H, 2-wire 4...20 mA HART+test button

Position 5 (Display, Operation)		
Selected option	Description	
FTL64	A	W/o; switch
	E	Graphic display with touch control
	F	Graphic display with touch control+Bluetooth

Position 6 (Housing, Material)		
Selected option	Description	
FTL64	B	Single compartment; Alu, coated
	M	Dual compartment L-shape; Alu, coated
	N	Dual compartment L-shape; 316L

Position 7 (Electrical Connection)		
Selected option	Description	
FTL64	A	Gland M20, plastic, IP66/68 NEMA Type 4X/6P
	B	Gland M20, brass nickel plated, IP66/68 NEMA Type 4X/6P
	C	Gland M20, 316L, IP66/68 NEMA Type 4X/6P
	F	Thread M20, IP66/68 NEMA Type 4X/6P
	G	Thread G1/2, IP66/68 NEMA Type 4X/6P
	H	Thread NPT1/2, IP66/68 NEMA Type 4X/6P
	M	Plug M12, IP66/67 NEMA Type 4X

<b>Position 8 (Application)</b>		
<b>Selected option</b>		<b>Description</b>
FTL64	D	Process max 280°C/536°F, max 100bar
	E	Process max 230°C/446°F, max 100bar
	R	Process max 230°C/446°F, max 40bar (PFA)
	9	Special version: Process max 300°C/572°F, max 100bar

<b>Position 9 (Surface Refinement)</b>		
<b>Selected option</b>		<b>Description</b>
FTL64	A	Standard Ra<3,2um/126uin
	R	Coating PFA (conductive)

### *Optional specifications*

<b>ID Jx, Kx (Test, Certificate, Declaration)</b>		
<b>Selected option</b>		<b>Description</b>
FTL64	JL	Ambient temperature -50°C/-58°F
	JN	Ambient temperature -52°C/-62°F

<b>ID Nx, Ox (Accessory Mounted)</b>		
<b>Selected option</b>		<b>Description</b>
FTL64	NA <sup>1)</sup>	Overvoltage protection

1) Only in connection with Position 6 = M, N

<b>ID Px, Rx (Accessory Enclosed)</b>		
<b>Selected option</b>		<b>Description</b>
FTL64	PA <sup>1)</sup>	Weather protection cover, 316L
	PB <sup>2)</sup>	Weather protection cover, plastic

1) Only in connection with Position 6 = M, N

2) Only in connection with Position 6 = B

**Safety instructions:**  
**General**

- The device is intended to be used in explosive atmospheres as defined in the scope of EN IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Devices suitable for zone separation (marked Ga/Gb or Da/Db) are always suitable for installation in the less critical zone (Gb or Db). Due to space limitations the corresponding marking maybe not indicated on the nameplate.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations
- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
  - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ..)
  - Of isolated capacities (e.g. isolated metallic plates)
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application and the temperature class.
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.

**Safety instructions:**  
**Special conditions**

Permitted ambient temperature range at the electronics enclosure:  
 $-40\text{ °C} \leq T_a \leq +70\text{ °C}$

- Limitations of the maximum ambient temperature at the electronics enclosure may be required dependent on device configuration, process temperatures and temperature classification.
- Details of limitations: →  12, "Temperature tables".
- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
  - Observe the danger of electrostatic charging and discharge.
  - Do not install in the vicinity of processes ( $\leq 0.5\text{ m}$ ) generating strong electrostatic charges.
- Avoid sparks caused by impact and friction.

*Optional specification, ID Px, Rx = PA*

Connect the weather protection cover to the local potential equalization.

*Optional specification, ID Px, Rx = PB*

Avoid electrostatic charging of the weather protection cover (e.g. friction, cleaning, maintenance, strong medium flow).

### Device group IIC

*Basic specification, Position 9 = R*


Due to the surface resistance 1 G $\Omega$  ([R] PFA-conductive), this coating is suitable without restrictions.

### Type of protection Ex db

The high-temperature part of the device (fork/pipe/process connection/temperature spacer) is designed in type of protection Ex db and has an Ex ia connection to the electronics insert.

The installation on the terminals of the device must always be carried out in type of protection Ex i.

### Safety instructions: Installation



A0025536

1

- A Zone 1
- 1 Tank; Zone 0, Zone 1
- 2 Electronic insert
- 3 Enclosure
- 4 Associated intrinsically safe power supply units
- 5 Potential equalization line
- 6 Local potential equalization

- After aligning (rotating) the enclosure, retighten the fixing screw.
- When the device is connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC and IIB, the type of protection changes to Ex ib IIC and Ex ib IIB.
- Continuous service temperature of the connecting cable:  $\geq T_a + 20$  K.
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- Observe the maximum process conditions according to the manufacturer's Operating Instructions.
- At high medium temperatures, note flange pressure load capacity as a factor of temperature.
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.
- Support extension tube of the device if a dynamic load is expected.
- Only use genuine spare parts from Endress+Hauser which are specified for the device.

### Accessory high pressure sliding sleeve

The high pressure sliding sleeve can be used for a continuous setting of the switch point and is suited for zone separation if mounted properly (see Operating Instructions).

### Intrinsic safety

- The device is only suitable for connection to certified, intrinsically safe equipment with explosion protection Ex ia / Ex ib.
- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least  $500 V_{\text{rms}}$ .

*Optional specification, ID Nx, OX = NA*

The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least  $290 V_{\text{rms}}$ .

### Potential equalization

Integrate the device into the local potential equalization.

*Optional specification, ID Px, Rx = PA*

Connect the weather protection cover to the local potential equalization.

## Safety instructions: Zone 0

When using under non-atmospheric pressures and non-atmospheric temperatures: The sensor part of the device approved for Zone 0 does not cause any ignition hazards.


**Safety instructions:**  
**Zone separation**  
**Zone 0, Zone 1**

The zone separation wall of the device is made of stainless steel or high corrosion-resistant alloy of thickness  $\geq 1$  mm.

**Explosion protection with heat insulation**

*Basic specification, Position 8 = D, E, R, 9*

- While observing the "temperature derating", the device is suitable for process temperatures up to 300 °C.
- When operating, ensure that you rule out contact between hot component surfaces and potentially explosive atmospheres beyond the limits of the corresponding temperature class. Suitable measures: e.g. thermal insulation at container and/or pipes.
- The temperature of 85 °C specified at the reference point may not be exceeded.
- To protect the electronics, observe the specified ambient temperature at the electronics enclosure.



A0025541

2

$T_a$  Ambient temperature

$T_p$  Process temperature

1 Sensor

2 Temperature class, e.g. T6

3 Enclosure

4 Reference point: max. +85 °C

5 E.g. thermal insulation

## Temperature tables



- The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
- Do not exceed the max. ambient temperature at the enclosure.



*Optional specification, ID Jx, Kx = JL*

Lower limit of the ambient temperature for explosion protection changes to  $-50\text{ °C}$ .

*Optional specification, ID Jx, Kx = JN*

Lower limit of the ambient temperature for explosion protection changes to  $-52\text{ °C}$ .

*Optional specification, ID Px, Rx = PB*

When using the weather protection cover: Reduce the admissible ambient temperature by 10 K.

*Basic specification, Position 8 = E, R*

*with Basic specification, Position 5 = A*

Temperature class	Process temperature range	Ambient temperature range
T6	$-60\text{ °C} \leq T_p \leq +80\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T5	$-60\text{ °C} \leq T_p \leq +95\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
T4	$-60\text{ °C} \leq T_p \leq +130\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T3	$-60\text{ °C} \leq T_p \leq +195\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
T2...T1	$-60\text{ °C} \leq T_p \leq +230\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$

*with Basic specification, Position 5 = E, F*

Temperature class	Process temperature range	Ambient temperature range
T6	$-60\text{ °C} \leq T_p \leq +80\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$
T5	$-60\text{ °C} \leq T_p \leq +95\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
T4	$-60\text{ °C} \leq T_p \leq +130\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
T3	$-60\text{ °C} \leq T_p \leq +195\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$
T2...T1	$-60\text{ °C} \leq T_p \leq +230\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$

*Basic specification, Position 8 = D, 9*

*with Basic specification, Position 5 = A*

Temperature class	Process temperature range	Ambient temperature range
T6	$-60\text{ °C} \leq T_p \leq +80\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T5	$-60\text{ °C} \leq T_p \leq +95\text{ °C}$	$-40\text{ °C} \leq T_a \leq +70\text{ °C}$
T4	$-60\text{ °C} \leq T_p \leq +130\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T3	$-60\text{ °C} \leq T_p \leq +195\text{ °C}$	$-40\text{ °C} \leq T_a \leq +65\text{ °C}$
T2	$-60\text{ °C} \leq T_p \leq +280\text{ °C}$ $-60\text{ °C} \leq T_p \leq +290\text{ °C}^{1)}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$ $-40\text{ °C} \leq T_a \leq +60\text{ °C}$
T1	$-60\text{ °C} \leq T_p \leq +300\text{ °C}^{1)}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$

1) Only in connection with Position 8 = 9

*with Basic specification, Position 5 = E, F*

Temperature class	Process temperature range	Ambient temperature range
T6	$-60\text{ °C} \leq T_p \leq +80\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$
T5	$-60\text{ °C} \leq T_p \leq +95\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
T4	$-60\text{ °C} \leq T_p \leq +130\text{ °C}$	$-40\text{ °C} \leq T_a \leq +60\text{ °C}$
T3	$-60\text{ °C} \leq T_p \leq +195\text{ °C}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$
T2	$-60\text{ °C} \leq T_p \leq +280\text{ °C}$ $-60\text{ °C} \leq T_p \leq +290\text{ °C}^{1)}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$ $-40\text{ °C} \leq T_a \leq +55\text{ °C}$
T1	$-60\text{ °C} \leq T_p \leq +300\text{ °C}^{1)}$	$-40\text{ °C} \leq T_a \leq +55\text{ °C}$

1) Only in connection with Position 8 = 9

## Connection data

Power supply
$U_i \leq 30\text{ V}_{DC}$ $I_i \leq 300\text{ mA}$ $P_i \leq 1\text{ W}$ $C_i \leq 10\text{ nF}$ $L_i = 0$







71588164

[www.addresses.endress.com](http://www.addresses.endress.com)

---