

## MCS200HW

# Proven measuring technology for flue gas monitoring

### Ready for current and future emission regulations

- Reliable measuring results – even for water-soluble gas components
- Only one analyzer necessary for simultaneous monitoring of up to 12 gas components
- Measurement components can be configured and extended flexibly – even in the field
- Convenient, task-oriented operation via touch display
- Remote access without additional software
- High availability due to certified internal reference point drift monitoring (QAL3) without test gases
- Low service costs thanks to minimal maintenance requirements
- Data transmission through only one interface possible
- Use in explosion-hazardous areas thanks to rugged, pressurized enclosure



# MCS200HW: Standard version


## Ready for current and future emission regulations

Strict legal limits apply to the flue gas emissions of industrial plants with combustion processes. With the MCS200HW analyzer system, emissions can be continuously monitored – accurately and very reliably. The MCS200HW simultaneously measures up to 10 infrared-active gas components such as SO<sub>2</sub>, NO, NO<sub>2</sub>, CO, CO<sub>2</sub>, NH<sub>3</sub>, N<sub>2</sub>O, H<sub>2</sub>O, HCl, CH<sub>4</sub> as well as O<sub>2</sub> and can be configured for customer-specific measuring tasks.

The state-of-the-art MCS200HW is easy to install, user-friendly, and requires only minimal maintenance, making it a highly cost-effective solution. The analyzer system is designed for industrial applications and features advanced interfaces for operation and communication. It can easily be extended with a GMS811 FIDORi FID measurement module for measuring total carbon concentrations. Thanks to its modular design, additional measuring components can be retrofitted even after the analyser has been installed in the field.

### Easy access to the device and secure data access

The 12" touch display on the front side of the analyzer cabinet provides a task-based interface for operating the entire MCS200HW analyzer system. The web-based operating concept enables device and location independent access – conveniently and securely – via a web browser. No installation of specific software is required.



### Secure data transmission via standardized Modbus® interface

The MCS200HW is certified according to the VDI 4201 standard, enabling seamless data transmission via a digital Modbus® interface. This significantly reduces installation and integration effort, as no special hardware such as analog or digital modules is required for communication with the device.



### Emission measurement in your plant

Legal environmental regulations require the continuous monitoring of numerous pollutants and reference values in the exhaust gases of industrial plants. The MCS200HW can continuously measure, at a heated extractive sample point, gas components such as: HCl, CO, NO<sub>x</sub> as the sum of NO and NO<sub>2</sub>, SO<sub>2</sub>, NH<sub>3</sub>, O<sub>2</sub>, H<sub>2</sub>O, CO<sub>2</sub> and TOC/C<sub>ges</sub>. For normalization, the pressure and temperature parameters are also recorded. The QAL3 thorough check can be carried out without test gas with the certified, integrated calibration filter.



### Monitoring of gas compositions

In industrial plants such as metal and steel works that optimize the combustion system of the finishing furnaces, it is possible to improve the furnace performance and thereby achieve long-term savings for the plant operator.

The MCS200HW does so by efficiently and very reliably measuring flue gases such as CO, CO<sub>2</sub>, H<sub>2</sub>O, NO, NO<sub>2</sub>, O<sub>2</sub> and SO<sub>2</sub> at the gas outlet of the furnace.



# MCS200HW: Ex-version


## Reliable emission measurement – including in explosion-hazardous areas



In industries with explosion-hazardous areas, a single spark can be disastrous. To meet the stringent requirements on explosion protection, analyzers and measuring devices must be especially rugged and reliable. The MCS200HW Ex is equipped with a pressurized enclosure for explosion-protection zones according to ATEX Zone 2 IIC T3. The touch display on the front side of the analyzer system – incorporated in the pressurized system – provides direct access to important functions and settings. And the SOPAS operating software provides a high level of transparency through convenient access from anywhere in your network.

### Rugged for harsh Ex conditions:

- Classification for ATEX Zone 2 IIC T3
- Standardized measuring technology for economical CEMS solutions
- Simple and time-saving operation via innovative 12" touch display
- Consistent operating software with access from anywhere within the connected network





### Emission measurements in petrochemical plants and refineries

Central supply equipment in any chemical plant includes boilers, furnaces and combustion systems. The amount and type of gas component emitted are regulated by local authorities in the form of environmental regulations and limit values. That is why  $O_2$ ,  $NO_x$ ,  $CO$ ,  $SO_2$ ,  $NH_3$ ,  $CH_4$ ,  $HCl$  and other substances often need to be continuously monitored. The appropriate analyzer solution is dependent on the type of fuel and the combustion process.



### Emission measurement in your plant

Hazardous zones in industries and plants are reclassified on a regular basis. MCS200HW Ex is a rugged and reliable solution with an industry tested and proven measurement technology in a pressurized enclosure version that meets ATEX Zone 2 requirements.





## One analyzer system, many possibilities, high efficiency

### Long service life and high measurement certainty

The MCS200HW works according to the measurement principle of an infrared single-beam photometer. Both interference and gas filter correlation methods are used. All parts in contact with the sample gas are heated above the dew point in order to prevent condensate formation in the analyzer system and to avoid damage due to corrosion. Thus, water-soluble gases such as HCl or NH<sub>3</sub> can be monitored and are not lost through salt formation.

### Reliable and cost-effective with very high measurement quality

Thanks to internal adjustment filters, drift checking and adjustment are possible even without a test gas. The reference point of all infrared-active components can be checked both manually and fully automatically. The reference point check can also be used for quality assurance during operation (QAL3 inspection). Expensive test gases are not necessary and the workload is reduced.



#### Low maintenance and effective: wear-free gas pumping

An ejector pump conveys the measurement gas from the gas sampling unit of the analyzer system. The device operates without wear and tear: the gas is moved in the system by negative pressure without mechanical stress on the components. Maintenance is minimized, which at the same time reduces running costs.

#### Tailored configuration for flexibility and efficiency

The analyzer system can be individually configured depending on the measuring task. The costs are based on the respective measuring components used. The result: tailored analyzer system – highly economical and high-performing.

Should future requirements call for the monitoring of additional pollutants, for example due to an updated plant permit, the analyser system can be expanded flexibly. New measuring components can be added on site, even after installation. This minimises both downtime and costs.

#### Lower costs due to the use of dry test gases

With the MCS200HW, reference point checking and adjustment of HCl and NH<sub>3</sub> are possible for the first time using exclusively dry test gases certified according to EN 15267 and EN 14181. Test gas generators or evaporators for generating wet test gases are no longer required. This saves time and reduces operating costs. Both for operating entities, e.g. when carrying out the regular QAL3 inspections, and for test institutes, e.g. when carrying out the annual surveillance test (AST).

# Condition monitoring included



## Condition Monitoring for maximum efficiency and fail-safety

If desired, the MCS200HW can be supplied from the factory with a pre-connected Monitoring Box and Condition Monitoring services. This enables the end user to visualize and evaluate the plant and analyzer systems condition data anytime, anywhere.

## Your benefit

You can deploy your maintenance staff immediately only when it's truly necessary, thereby minimizing both downtime and maintenance costs. Since reliable gas analysis is essential for continuous emission monitoring and process control, the Monitoring Box also helps you to ensure compliance with strict emission limits and availability requirements.




### Plan your service deployments efficiently with the Monitoring Box

With the Monitoring Box, you obtain virtual access to sensors and plants and can continuously optimize them during operation. The Monitoring Box digitally monitors all integrated devices of your company and detects any changes in the condition of sensors and plants in real time. Faults

can thereby be detected early or avoided altogether. The Monitoring Box not only supports predictive maintenance. It also makes it easier to prepare for service deployments so our service technicians can be on-site in time and with the right spare parts.

#### Step by step to more efficiency



#### Data analysis and trend forecasting

Diagrams present measurement data and the status of all devices in a clear and understandable way within the dashboard. This allows the data to be quickly analyzed and trends identified.



#### High plant availability

Analysis of condition data reduces unplanned downtimes and keeps the plant running smoothly.



#### Quick response

Automatic alerts in e-mails or text messages enable timely action when anomalies or deviations are detected. Solutions and recommended actions are displayed in direct form



#### Predictive maintenance

Verification and evaluation of historical data make it possible to schedule maintenance work and optimize the lifetime of spare and wear parts. This saves time and money.

# MCS200HW:

## Proven measurement technology for flue gas monitoring



### Product Description

The MCS200HW is a multi-component analyzer system for continuous monitoring of up to 10 IR measurement components in flue gases of industrial combustion plants. The MCS200HW operates using a hot-extractive method: all wetted parts, from the gas sampling probe to the cuvette, are heated above the dew

point and thus protected from corrosion. The internal reference point check enables a quick verification of measured values without test gases. The web display and task assistants integrated in the software make operation very easy. The MCS200HW Ex also provides reliable emission measurement in hazardous areas.

### At a glance

- Measurement of up to 10 IR components plus O<sub>2</sub> and TOC
- Hot/wet extractive measurement technology
- Wear-free gas distribution through ejector pumps
- Reference point monitoring with internal calibration cells
- Certified digital Modbus® interface
- Web server for platform-independent device control
- Use of dry test gases for HCl and NH<sub>3</sub>
- Classification for ATEX Zone 2 IIC T3

### Your benefits

- Reliable measurement results, even for water-soluble gas components
- Only one analyzer necessary for simultaneous monitoring of up to 12 gas components
- Measurement components can be configured and extended flexibly even in the field
- Convenient, task-oriented operation via touch display
- Remote access without additional software
- High availability due to certified internal reference point drift monitoring (QAL3) without test gases
- Low service costs thanks to minimal maintenance requirements
- Data transmission through only one interface possible
- Use in explosion-hazardous areas thanks to rugged, pressurized enclosure

### Fields of application

- Emission monitoring for waste incineration plants as well as power plants and plants with co-incineration, e.g. cement plants
- Measurement of nitrogen oxides (NO, NO<sub>2</sub>, N<sub>2</sub>O) in nitric acid plants
- Emission monitoring in sulfur recovery units with high SO<sub>2</sub> fluctuations



### More Information online

For more information, enter the link or scan the QR code to get direct access to technical data, operating instructions, software, application examples, and much more.

[www.endress.com/mcs200hw](http://www.endress.com/mcs200hw)



## Technical data

The precise device specifications and product performance data may vary and are dependent on the respective application and customer specifications.

### MCS200HW: standard version

Measured values	CH <sub>4</sub> , CO, CO <sub>2</sub> , C <sub>org</sub> , HCl, H <sub>2</sub> O, NH <sub>3</sub> , NO, NO <sub>2</sub> , N <sub>2</sub> O, O <sub>2</sub> , SO <sub>2</sub>
Performance-tested measurand	CH <sub>4</sub> , CO, CO <sub>2</sub> , C <sub>org</sub> , HCl, H <sub>2</sub> O, NH <sub>3</sub> , NO, NO <sub>2</sub> , N <sub>2</sub> O, O <sub>2</sub> , SO <sub>2</sub>
Measurement principles	interference filter correlation, gas filter correlation
Measuring distance	8.48 m
Gas flow rate	200 l/h to 400 l/h
Measuring ranges	
HCl	0 to 9 ppm / 0 to 1,840 ppm
NH <sub>3</sub>	0 to 9 ppm / 0 to 650 ppm
CO	0 to 24 ppm / 0 to 8,000 ppm
NO	0 to 37 ppm / 0 to 1,865 ppm
CH <sub>4</sub>	0 to 70 ppm / 0 to 700 ppm
NO <sub>2</sub>	0 to 25 ppm / 0 to 240 ppm
CO <sub>2</sub>	0 to 25 Vol.-% / 0 to 50 Vol.-%
SO <sub>2</sub>	0 to 26 ppm / 0 to 875 ppm
H <sub>2</sub> O	0 to 40 Vol.-%
O <sub>2</sub>	0 to 25 Vol.-%
N <sub>2</sub> O	0 to 23 ppm / 0 to 1,015 ppm
C <sub>org</sub> (TOC)	0 to 15 mg/m <sup>3</sup> / 0 to 10,000 mg/m <sup>3</sup>
Certified measuring ranges	
HCl	0 to 15 mg/m <sup>3</sup> / 0 to 3,000 mg/m <sup>3</sup>
NH <sub>3</sub>	0 to 10 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
NH <sub>3</sub> (low)	0 to 7 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
CO	0 to 75 mg/m <sup>3</sup> / 0 to 10,000 mg/m <sup>3</sup>
CO (low)	0 to 30 mg/m <sup>3</sup> / 0 to 10,000 mg/m <sup>3</sup>
NO	0 to 150 mg/m <sup>3</sup> / 0 to 2,500 mg/m <sup>3</sup>
NO (low)	0 to 50 mg/m <sup>3</sup> / 0 to 2,500 mg/m <sup>3</sup>
CH <sub>4</sub>	0 to 50 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
NO <sub>2</sub>	0 to 50 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
CO <sub>2</sub>	0 to 25% by vol.
SO <sub>2</sub>	0 to 75 mg/m <sup>3</sup> / 0 to 2,500 mg/m <sup>3</sup>
H <sub>2</sub> O	0 to 40% by vol.
O <sub>2</sub>	0 to 25% by vol.
N <sub>2</sub> O	0 to 100 mg/m <sup>3</sup> / 0 to 2,000 mg/m <sup>3</sup>
N <sub>2</sub> O (low)	0 to 45 mg/m <sup>3</sup> / 0 to 2,000 mg/m <sup>3</sup>
C <sub>org</sub> (TOC)	0 to 15 mg/m <sup>3</sup> / 0 to 50 mg/m <sup>3</sup> / 0 to 150 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>

Response time ( $t_{90}$ )	< 200 s
Accuracy	< 2% of the respective full scale value
Zero point drift	< 3% of the respective full scale value per maintenance interval
Reference point drift	< 3% of the respective full scale value per maintenance interval
Detection limit	< 2% of the respective full scale value
TOC measurement	0.05 mg/m <sup>3</sup>
Process temperature	≤ +550 °C
Sample gas temperature	
Input analyzer system:	≤ +200 °C
Process pressure	850 hPa to 1,100 hPa
Process gas humidity	≤ 40% by vol.
Ambient temperature	+5 °C to +40 °C
with A/C unit:	+5 °C to +50 °C
Storage temperature	-20 °C to +60 °C
Ambient pressure	850 hPa to 1,100 hPa
Ambient humidity	≤ 90% relative humidity; non-condensing
Conformities	Approved for systems requiring a permit: 2000/76 / EG (17 <sup>th</sup> German Federal Immission Control Act (BlmSchV)) 2001/80 / EC (13 <sup>th</sup> German Federal Immission Control Act (BlmSchV)) 27 <sup>th</sup> German Federal Immission Control Act (BlmSchV) EN 15267 EN 14181
Electrical safety	CE
Enclosure rating	IP54
Analog outputs	0/4 to 20 mA, 500 Ω; number depends on system configuration
Analog inputs	0/4 to 20 mA, 100 Ω; number depends on system configuration; electrically isolated
Digital outputs	48 V AC, 0.5 A, 35 W / 48 V DC, 0.5 A, 24 W; number depends on system configuration; electrically isolated
Digital inputs	3.9 V, 4.5 mA, 0.55 W; number depends on system configuration
Modbus	✓
Type of fieldbus integration	TCP RTU RS-485
PROFIBUS DP	✓
Note	Option
PROFINET	✓
Note	Option
Ethernet	✓
Function	Connection to SOPAS ET software or OPC server
Indication	LC display, status LEDs
Input	Touchscreen
Operation	Via LC display or SOPAS ET software, multiple operating levels, password-protected
Menu language	German, English

Dimensions (W x H x D)	
Analyzer cabinet	808 mm x 2.208 mm x 623 mm (details see dimensional drawings)
Mounting plate	699 mm x 1.896 mm x 334 mm (details see dimensional drawing)
Weight	
Analyzer cabinet	approx. 250 kg
Material system cabinet	Painted steel Option: stainless steel, GPR or without (mounting plate version)
Power supply	
Voltage	115 V AC, $\pm 10\%$ 230 V AC, $\pm 10\%$
Frequency	50 Hz / 60 Hz
Power consumption	Analyzer: $\leq 1,000$ VA Sample gas line, heated: $\leq 95$ VA/m Gas sampling unit: $\leq 450$ VA Heated gas sampling pipe: $\leq 200$ VA to $\leq 600$ VA
Auxiliaries	
Instrument air (zero gas quality):	$\leq 350$ l/h, 6 to 7 bar; particle size max. 5 $\mu\text{m}$ ; oil content max. 0.01 mg/m <sup>3</sup> ; pressure dew point max. $-40$ °C, purity class 2 (ISO 8573-1 [1:2:1])
Instrument air (propellant air for ejector):	$\leq 1,300$ l/h, 5 to 7 bar; particle size max. 5 $\mu\text{m}$ ; oil content max. 0.1 mg/m <sup>3</sup> ; pressure dew point max. $+3$ °C, purity class 3 (ISO 8573-1 [1:4:2])
Reference gas:	$\leq 350$ l/h, max. 4 bar; the reference gas must comply with the requirements of the applicable standards and guidelines
Sample connections	
Measuring gas input	Tube fitting connection for 6 mm pipes
Auxiliary connections	
Instrument air (zero gas quality)	DN 8/10
Propellant air for ejector	DN 6/8
Reference gas	Tube fitting connection for 6 mm pipes
Exhaust gas outlet	DN 8/10
Corrective functions	Drift correction and optical monitoring function via adjustment cell
Test functions	Automatic check cycle for zero and reference point
System components	Gas sampling unit Sample gas line Analyzer cabinet
Options	GMS811 FIDORi

## MCS200HW Ex system

Measured values	CH <sub>4</sub> , CO, CO <sub>2</sub> , HCl, H <sub>2</sub> O, NH <sub>3</sub> , NO, NO <sub>2</sub> , N <sub>2</sub> O, O <sub>2</sub> , SO <sub>2</sub>
Performance-tested measurand	CH <sub>4</sub> , CO, CO <sub>2</sub> , HCl, H <sub>2</sub> O, NH <sub>3</sub> , NO, NO <sub>2</sub> , N <sub>2</sub> O, O <sub>2</sub> , SO <sub>2</sub>
Measurement principles	interference filter correlation, gas filter correlation
Measuring distance	8.48 m
Gas flow rate	200 l/h to 400 l/h
Measuring ranges	
	HCl 0 to 9 ppm / 0 to 1,840 ppm
	NH <sub>3</sub> 0 to 9 ppm / 0 to 650 ppm
	CO 0 to 24 ppm / 0 to 8,000 ppm
	NO 0 to 37 ppm / 0 to 1,865 ppm
	CH <sub>4</sub> 0 to 70 ppm / 0 to 700 ppm
	NO <sub>2</sub> 0 to 25 ppm / 0 to 240 ppm
	CO <sub>2</sub> 0 to 25 Vol.-% / 0 to 50 Vol.-%
	SO <sub>2</sub> 0 to 26 ppm / 0 to 875 ppm
	H <sub>2</sub> O 0 to 40 Vol.-%
	O <sub>2</sub> 0 to 25 Vol.-%
	N <sub>2</sub> O 0 to 23 ppm / 0 to 1,015 ppm
Certified measuring ranges	
	HCl 0 to 15 mg/m <sup>3</sup> / 0 to 3,000 mg/m <sup>3</sup>
	NH <sub>3</sub> 0 to 10 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
	NH <sub>3</sub> (low) 0 to 7 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
	CO 0 to 75 mg/m <sup>3</sup> / 0 to 10,000 mg/m <sup>3</sup>
	CO (low) 0 to 30 mg/m <sup>3</sup> / 0 to 10,000 mg/m <sup>3</sup>
	NO 0 to 150 mg/m <sup>3</sup> / 0 to 2,500 mg/m <sup>3</sup>
	NO (low) 0 to 50 mg/m <sup>3</sup> / 0 to 2,500 mg/m <sup>3</sup>
	CH <sub>4</sub> 0 to 50 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
	NO <sub>2</sub> 0 to 50 mg/m <sup>3</sup> / 0 to 500 mg/m <sup>3</sup>
	CO <sub>2</sub> 0 to 25% by vol.
	SO <sub>2</sub> 0 to 75 mg/m <sup>3</sup> / 0 to 2,500 mg/m <sup>3</sup>
	H <sub>2</sub> O 0 to 40% by vol.
	O <sub>2</sub> 0 to 25% by vol.
	N <sub>2</sub> O 0 to 100 mg/m <sup>3</sup> / 0 to 2,000 mg/m <sup>3</sup>
	N <sub>2</sub> O (low) 0 to 45 mg/m <sup>3</sup> / 0 to 2,000 mg/m <sup>3</sup>
Response time (t <sub>90</sub> )	< 200 s
Accuracy	< 2% of the respective full scale value
Zero point drift	< 3% of the respective full scale value per maintenance interval
Reference point drift	< 3% of the respective full scale value per maintenance interval
Detection limit	< 2% of the respective full scale value

Process temperature		≤ +550 °C
Sample gas temperatur		
Input analyzer system:		≤ +200 °C
Process pressure		850 hPa to 1,100 hPa
Process gas humidity		≤ 40% by vol.
Ambient temperature		-20 °C...+50 °C
Storage temperature		-20 °C to +55 °C
Ambient pressure		850 hPa to 1,100 hPa
Ambient humidity		≤ 90% relative humidity; non-condensing
Conformities		EN15267 EN14181
Ex-approvals		
	ATEX	3G IIC T3 Gc: Analyzer cabinet 3G IIC T3 Gc: Gas sampling unit 2G IIC T3 Gb: Sample gas line
Electrical safety		CE
Enclosure rating		IP65
Analog outputs		0/4 ... 20 mA, 500 Ω; number depends on system configuration
Analog inputs		0/4 to 20 mA, 100 Ω; number depends on system configuration; electrically isolated
Digital outputs		48 V AC, 0.5 A, 35 W / 48 V DC, 0.5 A, 24 W; number depends on system configuration; electrically isolated
Digital inputs		3.9 V, 4.5 mA, 0.55 W; number depends on system configuration
Modbus		✓
Type of fieldbus integration		TCP RTU RS-485
PROFIBUS DP		✓
	Note	Option
PROFINET		✓
	Note	Option
Ethernet		✓
Function		Connection to SOPAS ET software or OPC server
Indication		LC display, status LEDs
Input		Touchscreen
Operation		Via LC display or SOPAS ET software, multiple operating levels, password-protected
Menu language		German, English
Dimensions (W x H x D)		
	Analyzer cabinet	1,000 mm x 2,100 mm x 652 mm (details see dimensional drawings)
Weight		
	Analyzer cabinet	approx. 400 kg
Material system cabinet		Stainless steel Option: painted steel, GRP


Power supply	
Voltage	115 V AC, $\pm 10\%$ 230 V AC, $\pm 10\%$
Frequency	50 Hz / 60 Hz
Power consumption	Analyzer: $\leq 1,000$ VA Sample gas line, heated: $\leq 90$ VA/m Gas sampling unit: $\leq 600$ VA
Auxiliaries	
Instrument air (purge unit):	39.3 m <sup>3</sup> /h during pre-purging, $\leq 2$ m <sup>3</sup> /h during normal operation, 2.5 ... 4.5 bar, particle size max. 40 $\mu\text{m}$ ; oil content; max. 1 mg/m <sup>3</sup> ; pressure dew point max. $-20$ °C (ISO 8573-1 [5:3:3])
Instrument air (zero gas quality):	$\leq 350$ l/h, 6 to 7 bar; particle size max. 5 $\mu\text{m}$ ; oil content max. 0.01 mg/m <sup>3</sup> ; pressure dew point max. $-40$ °C, purity class 2 (ISO 8573-1 [1:2:1])
Instrument air (propellant air for ejector):	$\leq 1,300$ l/h, 5 to 7 bar; particle size max. 5 $\mu\text{m}$ ; oil content max. 0.1 mg/m <sup>3</sup> ; pressure dew point max. $+3$ °C, purity class 3 (ISO 8573-1 [1:4:2])
Reference gas:	$\leq 350$ l/h, max. 4 bar; the reference gas must comply with the requirements of the applicable standards and guidelines
Sample connections	
Measuring gas input	Tube fitting connection for 8 mm pipes
Auxiliary connections	
Instrument air:	Tube fitting for 10 mm pipes
Reference gas	Tube fitting connection for 6 mm pipes
Exhaust gas outlet	Tube fitting for 10 mm pipes
Corrective functions	Drift correction and optical monitoring function via adjustment cell
Test functions	Automatic check cycle for zero and reference point
System components	Gas sampling unit Sample gas line Analyzer cabinet

# Order information


Our regional sales organization will be glad to advise you on which device configuration is best for you.

## Dimensional drawings


MCS200HW standard version (dimensions in mm (inch))



# MCS200HW Ex system (dimensions in mm (inch))



## MCS200HW mounting plate (dimensions in mm (inch))



## Accessories

### Digital services for integration

#### Short description

- **Application:** Condition Monitoring
- **Description:** The Monitoring Box Basic is a scalable digital service for monitoring service and process data.
- **Hosting:** Off-premise: [monitoringbox.endress.com](https://monitoringbox.endress.com), On-premise: Industrial PC or virtual machine on the user's servers
- **Type:** App
- **Contract type:** SaaS
- **Contract interval:** Annual
- **Supported products:** MCS200HW
- **Vital data:** Operational status, Logbook, temperatures, Optical unit, Printed-circuit board assembly, Operating voltage, Frequencies, Drifts
- **Version:** Release 1

#### Type

Monitoring Box  
MCS200HW Basic

#### Part no.

1616023

[www.addresses.endress.com](http://www.addresses.endress.com)

---

Eco-friendly produced and printed on paper  
from sustainable forestry.

IND1366C/90/EN/04\_26-00  
8029956 / EN / V2-2