

# Technical Information

## Proline Prowirl R 200

Vortex flowmeter



### Flowmeter with best-in-class accuracy despite pipe reduction

#### Application

- Preferred measuring principle for wet steam/saturated steam, superheated steam, gases & liquid (including cryogenic applications)
- Specially designed for applications with very low flow or reduced flow

#### Device properties

- Integrated nominal diameter reduction by 1-2 sizes
- Nominal diameters (mating pipe) up to DN 250 (10")
- Flexible alignment of the pressure measuring cell
- Display module with data transfer function
- Robust dual-compartment housing
- Plant safety: worldwide approvals (SIL, Haz. area)

#### Your benefits

- Energy management made easy – integrated temperature and pressure measurement for steam and gases
- Cost and time savings – no mating pipe changes required to reduce nominal diameter
- Consistent measurement accuracy up to Re 10 000 – Vortex meter body with unique linearity
- Long-term stability – robust, drift-free capacitance sensor
- Convenient wiring – separate connection compartment, various Ethernet options
- Safe operation – no need to open the device thanks to display with touch control, background lighting
- Built-in verification – Heartbeat Technology

## Table of contents

<b>About this document</b> . . . . .	<b>4</b>	Climate class . . . . .	56
Symbols . . . . .	4	Degree of protection . . . . .	56
<b>Function and system design</b> . . . . .	<b>5</b>	Vibration-resistance and shock resistance . . . . .	56
Measuring principle . . . . .	5	Electromagnetic compatibility (EMC) . . . . .	57
Measuring system . . . . .	9	<b>Process</b> . . . . .	<b>57</b>
<b>Input</b> . . . . .	<b>10</b>	Medium temperature range . . . . .	57
Measured variable . . . . .	10	Pressure/temperature ratings . . . . .	58
Measuring range . . . . .	11	Nominal pressure of sensor . . . . .	60
Operable flow range . . . . .	16	Pressure specifications . . . . .	60
Input signal . . . . .	16	Pressure loss . . . . .	60
<b>Output</b> . . . . .	<b>18</b>	Thermal insulation . . . . .	60
Output signal . . . . .	18	<b>Mechanical construction</b> . . . . .	<b>61</b>
Signal on alarm . . . . .	20	Dimensions in SI units . . . . .	61
Load . . . . .	22	Dimensions in US units . . . . .	78
Ex connection data . . . . .	23	Weight . . . . .	87
Low flow cut off . . . . .	29	Materials . . . . .	91
Galvanic isolation . . . . .	29	Flange connections . . . . .	94
Protocol-specific data . . . . .	29	<b>Operability</b> . . . . .	<b>95</b>
<b>Power supply</b> . . . . .	<b>32</b>	Operating concept . . . . .	95
Terminal assignment . . . . .	32	Languages . . . . .	95
Pin assignment, device plug . . . . .	35	Onsite operation . . . . .	95
Supply voltage . . . . .	35	Remote operation . . . . .	96
Power consumption . . . . .	36	Service interface . . . . .	98
Current consumption . . . . .	37	Supported operating tools . . . . .	99
Power supply failure . . . . .	37	<b>Certificates and approvals</b> . . . . .	<b>100</b>
Electrical connection . . . . .	38	CE mark . . . . .	100
Potential equalization . . . . .	41	UKCA marking . . . . .	100
Terminals . . . . .	41	RCM marking . . . . .	100
Cable entries . . . . .	41	Ex approval . . . . .	100
Cable specification . . . . .	41	Functional safety . . . . .	100
Overvoltage protection . . . . .	43	HART certification . . . . .	101
<b>Performance characteristics</b> . . . . .	<b>43</b>	FOUNDATION Fieldbus certification . . . . .	101
Reference operating conditions . . . . .	43	Certification PROFIBUS . . . . .	101
Maximum measurement error . . . . .	43	PROFINET over Ethernet-APL certification . . . . .	101
Repeatability . . . . .	47	Pressure Equipment Directive . . . . .	101
Response time . . . . .	48	Experience . . . . .	101
Relative humidity . . . . .	48	External standards and guidelines . . . . .	102
Operating height . . . . .	48	<b>Ordering information</b> . . . . .	<b>102</b>
Influence of ambient temperature . . . . .	48	Product generation index . . . . .	102
<b>Installation</b> . . . . .	<b>49</b>	<b>Application packages</b> . . . . .	<b>103</b>
Mounting location . . . . .	49	Diagnostic functionality . . . . .	103
Orientation . . . . .	49	Heartbeat Technology . . . . .	103
Inlet and outlet runs . . . . .	51	<b>Accessories</b> . . . . .	<b>103</b>
Length of connecting cable . . . . .	53	Device-specific accessories . . . . .	104
Mounting the transmitter housing . . . . .	54	Communication-specific accessories . . . . .	105
Installation for delta heat measurements . . . . .	54	Service-specific accessories . . . . .	106
Protective cover . . . . .	55	System components . . . . .	107
<b>Environment</b> . . . . .	<b>55</b>		
Ambient temperature range . . . . .	55		
Storage temperature . . . . .	56		






**Documentation . . . . . 107**  
Standard documentation . . . . . 107  
Supplementary device-dependent documentation . . . . . 108

**Registered trademarks . . . . . 109**



## About this document

### Symbols









#### Electrical symbols

Symbol	Meaning
	Direct current
	Alternating current
	Direct current and alternating current
	<b>Ground connection</b> A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	<b>Potential equalization connection (PE: Protective earth)</b> Ground terminals that must be connected to ground prior to establishing any other connections.  The ground terminals are located on the interior and exterior of the device: <ul style="list-style-type: none"> <li>Interior ground terminal: potential equalization connection is connected to the supply network.</li> <li>Exterior ground terminal: device is connected to the plant grounding system.</li> </ul>

#### Communication-specific symbols




Symbol	Meaning
	<b>Wireless Local Area Network (WLAN)</b> Communication via a wireless, local network.
	<b>Bluetooth</b> Wireless data transmission between devices over a short distance via radio technology.

#### Symbols for certain types of information

Symbol	Meaning
	<b>Permitted</b> Procedures, processes or actions that are permitted.
	<b>Preferred</b> Procedures, processes or actions that are preferred.
	<b>Forbidden</b> Procedures, processes or actions that are forbidden.
	<b>Tip</b> Indicates additional information.
	Reference to documentation
	Reference to page
	Reference to graphic
	Visual inspection

#### Symbols in graphics


Symbol	Meaning
1, 2, 3, ...	Item numbers
<b>1</b> , <b>2</b> , <b>3</b> , ...	Series of steps

Symbol	Meaning
A, B, C, ...	Views
A-A, B-B, C-C, ...	Sections
	Hazardous area
	Safe area (non-hazardous area)
	Flow direction

## Function and system design

### Measuring principle

Vortex meters work on the principle of the *Karman vortex street*. When fluid flows past a bluff body, vortices are alternately formed on both sides with opposite directions of rotation. These vortices each generate a local low pressure. The pressure fluctuations are recorded by the sensor and converted to electrical pulses. The vortices develop very regularly within the permitted application limits of the device. Therefore, the frequency of vortex shedding is proportional to the volume flow.



A0033465

 1 Sample graphic

The calibration factor (K-factor) is used as the proportional constant:

$$\text{K-Factor} = \frac{\text{Pulses}}{\text{Unit Volume [m}^3\text{]}}$$

A0003939-EN

Within the application limits of the device, the K-factor only depends on the geometry of the device. For  $Re > 10\,000$  it is:

- Independent of the flow velocity and the fluid properties viscosity and density
- Independent of the type of substance under measurement: steam, gas or liquid

The primary measuring signal is linear to the flow. After production, the K-factor is determined in the factory by means of calibration. It is not subject to long-time drift or zero-point drift.

The device does not contain any moving parts and does not require any maintenance.

### The capacitance sensor

The sensor of a vortex flowmeter has a major influence on the performance, robustness and reliability of the entire measuring system.

The robust DSC sensor is:

- burst-tested
- tested against vibrations
- tested against thermal shock (thermal shocks of 150 K/s)

The measuring device uses the tried-and-tested, capacitance measuring technology from Endress+Hauser, which is already in use in over 450 000 measuring points worldwide. Thanks to its design, the capacitance sensor is also particularly mechanically resistant to temperature shocks and pressure shocks in steam pipelines.


#### Temperature measurement

The "mass" option is available under the order code for "Sensor version". With this option the measuring device can also measure the temperature of the medium.

The temperature is measured via Pt 1000 temperature sensors. These are located in the paddle of the DSC sensor and are therefore in the direct vicinity of the fluid.

Order code for "Sensor version; DSC sensor; measuring tube":

- Option AA "volume; 316L; 316L"
- Option AB "volume; Alloy C22; 316L"
- Option BA "volume high-temperature; 316L; 316L"
- Option BB "volume high-temperature; Alloy C22; 316L"
- Option CA "Mass; 316L; 316L (integrated temperature measurement)"
- Option CB "Mass; Alloy C22; 316L (integrated temperature measurement)"



- 1 Order code for "Sensor version", option "volume" or "volume high-temperature"  
 2 Order code for "Sensor version", option "mass"

#### Pressure and temperature measurement

**i** For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:

- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.

The "mass steam" or "mass gas/liquid" options are available under the order code for "Sensor version; DSC sensor; measuring tube". With these options, the measuring instrument can also measure the pressure and temperature of the fluid.

The temperature is measured via Pt 1000 temperature sensors. These are located in the paddle of the DSC sensor and are therefore in the direct vicinity of the fluid. Pressure measurement is located directly on the meter body at the level of the bluff body. The position of the pressure tapping was chosen so that pressure and temperature could be measured at the same point. This enables accurate density and/or energy compensation of the fluid using pressure and temperature. The measured pressure tends to be somewhat lower than the line pressure. For this reason, Endress+Hauser offers a correction to the line pressure (integrated in the device).

Order code for "Sensor version; DSC sensor; measuring tube":

- Option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement)"
- Option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement)"

### Lifelong calibration

Experience has shown that recalibrated measuring devices demonstrate a very high degree of stability compared to their original calibration: The recalibration values were all within the original measuring accuracy specifications of the devices. This applies to the measured volume flow, the device's primary measured variable.

Various tests and simulation have shown that once the radii of the edges on the bluff body are less than 1 mm (0.04 in), the resulting effect does not have a negative impact on accuracy.


If the radii of the edges on the bluff body do not exceed 1 mm (0.04 in), the following general statements apply (in the case of non-abrasive and non-corrosive media, such as in most water and steam applications):

- The measuring device does not display an offset in the calibration and the accuracy is still guaranteed.
- All the edges on the bluff body have a radius that is typically smaller in size. As the measuring devices are naturally also calibrated with these radii, the measuring device remains within the specified accuracy rating provided that the additional radius that is produced as a result of wear and tear does not exceed 1 mm (0.04 in).


Consequently, it can be said that the product line offers lifelong calibration if the measuring device is used in non-abrasive and non-corrosive media.

### Sensors with integrated nominal diameter reduction

In many applications the nominal diameter of the customer's pipe does not match the nominal diameter that is optimum for a vortex meter. As a result, the flow velocity is too low for vortex formation after the bluff body. This is expressed in signal loss in the lower flow range. The flow velocity can be increased by reducing the nominal diameter by one or two sizes. This enables the installation of the following adapters:



A0034060



A0019070

A Nominal diameter reduction by installing various adapters and pipe segments in the pipe

B Nominal diameter reduction by using the Prowirl with integrated line size reduction

1 Reducer element

2 Straight pipe segment as the inlet run (min.  $15 \times DN$ ) upstream from the vortex meter

3 Straight pipe segment as the outlet run (min.  $5 \times DN$ ) downstream from the vortex meter

4 Expansion element

Name of Prowirl vortex flowmeters with integrated nominal diameter reduction:

- Prowirl R 200 "R-type": with single inner diameter line size reduction, e.g. from DN 80 (3") to DN 50 (2")
- Prowirl R 200 "S-type": with double inner diameter line size reduction, e.g. from DN 80 (3") to DN 40 (1½")

These models offer the following benefits:

Savings in terms of cost and time: the additional adapters are replaced entirely by one single device

- Measuring range extended for lower flow rates
- Lower risk in the planning phase as same lengths are used compared to standard flanged devices
- All device types can be used alternatively without the need for complicated changes to the layout
- Accuracy specifications identical to those for standard devices



Inlet and outlet runs to be considered → 51

### Air and industrial gases

The measuring device enables users to calculate the density and energy of air and industrial gases. The calculations are based on time-tested standard calculation methods. It is possible to automatically compensate for the effect of pressure and temperature via an external or constant value.

This makes it possible to output the energy flow, standard volume flow and mass flow of the following gases:

- Single gas
- Gas mixture
- Air
- User-specific gas



For detailed information on the parameters, see the Operating Instructions. → 107

### Natural gas

The device enables users to calculate the chemical properties (gross calorific value, net calorific value) of natural gases. The calculations are based on time-tested standard calculation methods. It is possible to automatically compensate for the effect of pressure and temperature via an external or constant value.

This makes it possible to output the energy flow, standard volume flow and mass flow in accordance with the following standard methods:

Energy can be calculated based on the following standards:

- AGA5
- ISO 6976
- GPA 2172

Density can be calculated based on the following standards:

- ISO 12213-2 (AGA8-DC92)
- ISO 12213-3
- AGA NX19
- AGA8 Gross 1
- SGERG 88



For detailed information on the parameters, see the Operating Instructions. → 107




Measuring system

The device consists of a transmitter and a sensor.


Two device versions are available:

- Compact version - transmitter and sensor form a mechanical unit.
- Remote version - transmitter and sensor are mounted in separate locations.


Transmitter


<p><b>Proline 200</b></p>  <p>A0013471</p>	<p>Device versions and materials:</p> <ul style="list-style-type: none"><li>■ Compact or remote version, aluminum coated: Aluminum, AlSi10Mg, coated</li><li>■ Compact or remote version, stainless: For maximum corrosion resistance: stainless steel CF3M</li></ul> <p>Configuration:</p> <ul style="list-style-type: none"><li>■ Via four-line local display with key operation or via four-line, illuminated local display with touch control and guided menus ("Make-it-run" wizards) for applications</li><li>■ Via operating tools (e.g. FieldCare)</li></ul>
---	--

Sensor

<p><b>Prowirl R</b></p>  <p>A0034075</p>	<p>Flanged version with integrated nominal diameter reduction:</p> <ul style="list-style-type: none"><li>■ Two versions with a different nominal diameter range are available:<ul style="list-style-type: none"><li>■ "R-type" with single inner diameter line size reduction: DN 25R to 200R (1R to 8R")</li><li>■ "S-type" with double inner diameter line size reduction: DN 40S to 250S (1½S to 10S")</li></ul></li><li>■ Materials:<ul style="list-style-type: none"><li>■ Measuring tubes DN 15 to 150 (½ to 6"): stainless cast steel, CF3M/ 1.4408</li><li>■ Flange connections: stainless steel, triple-certified material, 1.4404/ F316/F316L</li></ul></li></ul>
--	---

Pressure measuring cell

-  For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:
- Only available for measuring instruments with the following communication protocols:
    - HART
    - PROFINET over Ethernet-APL
  - Oil-free or grease-free cleaning is not possible.

 <p>1 2</p> <p>A0034080</p> <p>1 Option DA "Mass steam" 2 Option DB "Mass gas/liquid"</p>	<p>Versions:</p> <p>Pressure components</p> <ul style="list-style-type: none"><li>■ Pressure measuring cell 2 bar_a</li><li>■ Pressure measuring cell 4 bar_a</li><li>■ Pressure measuring cell 10 bar_a</li><li>■ Pressure measuring cell 40 bar_a</li></ul> <p>Material</p> <ul style="list-style-type: none"><li>■ Wetted parts:<ul style="list-style-type: none"><li>■ Process connection Stainless steel, 1.4404/316L</li><li>■ Membrane Stainless steel, 1.4435/316L</li></ul></li><li>■ Non-wetted parts: Housing Stainless steel ,1.4404</li></ul>
--	--

# Input

## Measured variable

### Direct measured variables

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Measured variable
AA	Volume; 316L; 316L	Volume flow
AB	Volume; Alloy C22; 316L	
BA	Volume high-temperature; 316L; 316L	
BB	Volume high-temperature; Alloy C22; 316L	

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Measured variable
CA	Mass; 316L; 316L (integrated temperature measurement)	<ul style="list-style-type: none"> <li>■ Volume flow</li> <li>■ Temperature</li> </ul>
CB	Mass; Alloy C22; 316L (integrated temperature measurement)	



For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:

- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Measured variable
DA	Mass steam; 316L; 316L (integrated pressure/temperature measurement)	<ul style="list-style-type: none"> <li>■ Volume flow</li> <li>■ Temperature</li> <li>■ Pressure</li> </ul>
DB	Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement)	

### Calculated measured variables

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Measured variable
AA	Volume; 316L; 316L	Under constant process conditions: <ul style="list-style-type: none"> <li>■ Mass flow <sup>1)</sup></li> <li>■ Corrected volume flow</li> </ul>
AB	Volume; Alloy C22; 316L	
AC	Volume; Alloy C22; Alloy C22	The totalized values for: <ul style="list-style-type: none"> <li>■ Volume flow</li> <li>■ Mass flow</li> <li>■ Corrected volume flow</li> </ul>
BA	Volume high-temperature; 316L; 316L	
BB	Volume high-temperature; Alloy C22; 316L	

- 1) A fixed density must be entered for calculating the mass flow (**Setup** menu → **Advanced setup** submenu → **External compensation** submenu → **Fixed density** parameter).

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Measured variable
CA	Mass; 316L; 316L (integrated temperature measurement)	<ul style="list-style-type: none"> <li>■ Corrected volume flow</li> <li>■ Mass flow</li> <li>■ Calculated saturated steam pressure</li> <li>■ Energy flow</li> <li>■ Heat flow difference</li> <li>■ Specific volume</li> <li>■ Degrees of superheat</li> </ul>
CB	Mass; Alloy C22; 316L (integrated temperature measurement)	
CC	Mass; Alloy C22; Alloy C22 (integrated temperature measurement)	
DA	Mass steam; 316L; 316L (integrated pressure/temperature measurement)	
DB	Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement)	

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Measured variable
AA	Volume; 316L; 316L	Under constant process conditions:
AB	Volume; Alloy C22; 316L	
BA	Volume high-temperature; 316L; 316L	The totalized values for:
BB	Volume high-temperature; Alloy C22; 316L	

- 1) A fixed density must be entered for calculating the mass flow (**Setup** menu → **Advanced setup** submenu → **External compensation** submenu → **Fixed density** parameter).

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Measured variable
CA	Mass; 316L; 316L (integrated temperature measurement)	<ul style="list-style-type: none"> <li>■ Corrected volume flow</li> <li>■ Mass flow</li> <li>■ Calculated saturated steam pressure</li> <li>■ Energy flow</li> <li>■ Heat flow difference</li> <li>■ Specific volume</li> <li>■ Degrees of superheat</li> </ul>
CB	Mass; Alloy C22; 316L (integrated temperature measurement)	
DA	Mass steam; 316L; 316L (integrated pressure/temperature measurement)	
DB	Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement)	

## Measuring range

The measuring range is dependent on the nominal diameter, the fluid and environmental influences.



The following specified values are the largest possible flow measuring ranges ( $Q_{\min}$  to  $Q_{\max}$ ) for each nominal diameter. Depending on the fluid properties and environmental influences, the measuring range may be subject to additional restrictions. Additional restrictions apply to both the lower range value and the upper range value.


### Flow measuring ranges in SI units

DN [mm]	Liquids [m³/h]	Gas/steam [m³/h]
25R, 40S	0.1 to 4.9	0.52 to 25
40R, 50S	0.32 to 15	1.6 to 130
50R, 80S	0.78 to 37	3.9 to 310
80R, 100S	1.3 to 62	6.5 to 820
100R, 150S	2.9 to 140	15 to 1800
150R, 200S	5.1 to 240	25 to 3200
200R, 250 S	11 to 540	57 to 7300

## Flow measuring ranges in US units

DN	Liquids	Gas/steam
[in]	[ft <sup>3</sup> /min]	[ft <sup>3</sup> /min]
1R, 1½S	0.061 to 2.9	0.31 to 15
1½R, 2S	0.19 to 8.8	0.93 to 74
2R, 3S	0.46 to 22	2.3 to 180
3R, 4S	0.77 to 36	3.8 to 480
4R, 6S	1.7 to 81	8.6 to 1 100
6R, 8S	3 to 140	15 to 1 900
8R, 10S	6.8 to 320	34 to 4 300

## Flow velocity



A0033468

$D_i$  Measuring tube internal diameter (corresponds to dimension K → 61)

$v$  Velocity in measuring tube

$Q$  Flow



The internal diameter of measuring tube  $D_i$  is denoted in the dimensions as dimension K → 61.

Calculation of flow velocity:

$$v \text{ [m/s]} = \frac{4 \cdot Q \text{ [m}^3/\text{h}]}{\pi \cdot D_i \text{ [m]}^2} \cdot \frac{1}{3600 \text{ [s/h]}}$$

$$v \text{ [ft/s]} = \frac{4 \cdot Q \text{ [ft}^3/\text{min}]}{\pi \cdot D_i \text{ [ft]}^2} \cdot \frac{1}{60 \text{ [s/min]}}$$

A0034301

## Lower range value

## Reynolds number

A restriction applies to the lower range value due to the turbulent flow profile, which only occurs with Reynolds numbers greater than 5 000. The Reynolds number is dimensionless and indicates the ratio of the inertia force of a fluid to its viscous force when flowing and is used as a characteristic variable for pipe flows. In the case of pipe flows with Reynolds numbers less than 5 000, periodic vortices are no longer generated and flow rate measurement is no longer possible.

The Reynolds number is calculated as follows:

$$Re = \frac{4 \cdot Q \text{ [m}^3/\text{s}] \cdot \rho \text{ [kg/m}^3\text{]}}{\pi \cdot D_i \text{ [m]} \cdot \mu \text{ [Pa} \cdot \text{s]}}$$

$$Re = \frac{4 \cdot Q \text{ [ft}^3/\text{s}] \cdot \rho \text{ [lbm/ft}^3\text{]}}{\pi \cdot D_i \text{ [ft]} \cdot \mu \text{ [lbf} \cdot \text{s/ft}^2\text{]}}$$

A0034291

$Re$  Reynolds number

$Q$  Flow

$D_i$  Internal diameter of measuring tube (corresponds to dimension  $K \rightarrow$  61)

$\mu$  Dynamic viscosity

$\rho$  Density

The Reynolds number 5 000, together with the density and viscosity of the fluid and the nominal diameter, is used to calculate the corresponding flow rate.

$$Q_{Re=5000} \text{ [m}^3/\text{h}] = \frac{5000 \cdot \pi \cdot D_i \text{ [m]} \cdot \mu \text{ [Pa} \cdot \text{s]}}{4 \cdot \rho \text{ [kg/m}^3\text{]}} \cdot 3600 \text{ [s/h]}$$

$$Q_{Re=5000} \text{ [ft}^3/\text{h}] = \frac{5000 \cdot \pi \cdot D_i \text{ [ft]} \cdot \mu \text{ [lbf} \cdot \text{s/ft}^2\text{]}}{4 \cdot \rho \text{ [lbm/ft}^3\text{]}} \cdot 60 \text{ [s/min]}$$

A0034302

$Q_{Re=5000}$  Flow rate is dependent on the Reynolds number

$D_i$  Internal diameter of measuring tube (corresponds to dimension  $K \rightarrow$  61)

$\mu$  Dynamic viscosity

$\rho$  Density

#### Minimum measurable flow velocity based on signal amplitude

The measuring signal must have a certain minimum signal amplitude so that the signals can be evaluated without any errors. Using the nominal diameter, the corresponding flow can also be derived from this amplitude.

The minimum signal amplitude depends on the setting for the sensitivity of the DSC sensor, the steam quality **x** and the force of the vibrations present **a**.

The value **mf** corresponds to the lowest measurable flow velocity without vibration (no wet steam) for a density of 1 kg/m<sup>3</sup> (0.0624 lbm/ft<sup>3</sup>).

The value **mf** can be set in the range of 20 to 6 m/s (6 to 1.8 ft/s) (factory setting 12 m/s (3.7 ft/s)) with the **Sensitivity** parameter (value range 1 to 9, factory setting 5).

The lowest flow velocity that can be measured on account of the signal amplitude **v<sub>AmpMin</sub>** is derived from the **Sensitivity** parameter and steam quality **x** or from the force of vibrations present **a**.

$$v_{\text{AmpMin}} [\text{m/s}] = \max \left\{ \begin{array}{l} \frac{mf [\text{m/s}]}{x^2 \cdot \sqrt{\frac{\rho [\text{kg/m}^3]}{1 [\text{kg/m}^3]}}} \\ \frac{\sqrt{50 [\text{m}] \cdot a [\text{m/s}^2]}}{x^2} \end{array} \right.$$

$$v_{\text{AmpMin}} [\text{ft/s}] = \max \left\{ \begin{array}{l} \frac{mf [\text{ft/s}]}{x^2 \cdot \sqrt{\frac{\rho [\text{lbm/ft}^3]}{0.0624 [\text{lbm/ft}^3]}}} \\ \frac{\sqrt{164 [\text{ft}] \cdot a [\text{ft/s}^2]}}{x^2} \end{array} \right.$$

A0034309

$v_{\text{AmpMin}}$  Minimum measurable flow velocity based on signal amplitude

$mf$  Sensitivity

$x$  Steam quality

$\rho$  Density

Minimum measurable flow rate based on signal amplitude

$$Q_{\text{AmpMin}} [\text{m}^3/\text{h}] = \frac{v_{\text{AmpMin}} [\text{m/s}] \cdot \pi \cdot (D_i [\text{m}])^2}{4} \cdot 3600 [\text{s/h}]$$

$$Q_{\text{AmpMin}} [\text{ft}^3/\text{min}] = \frac{v_{\text{AmpMin}} [\text{ft/s}] \cdot \pi \cdot (D_i [\text{ft}])^2}{4} \cdot 60 [\text{s/min}]$$

A0034304

$Q_{\text{AmpMin}}$  Minimum measurable flow rate based on signal amplitude

$v_{\text{AmpMin}}$  Minimum measurable flow velocity based on signal amplitude

$D_i$  Internal diameter of measuring tube (corresponds to dimension  $K \rightarrow$  61)

$\rho$  Density

Effective lower range value

The effective lower range value  $Q_{\text{Low}}$  is determined using the largest of the three values  $Q_{\text{min}}$ ,  $Q_{\text{Re}} = 5000$  and  $Q_{\text{AmpMin}}$ .

$$Q_{\text{Low}} [\text{m}^3/\text{h}] = \max \left\{ \begin{array}{l} Q_{\text{min}} [\text{m}^3/\text{h}] \\ Q_{\text{Re} = 5000} [\text{m}^3/\text{h}] \\ Q_{\text{AmpMin}} [\text{m}^3/\text{h}] \end{array} \right.$$

$$Q_{\text{Low}} [\text{ft}^3/\text{min}] = \max \left\{ \begin{array}{l} Q_{\text{min}} [\text{ft}^3/\text{min}] \\ Q_{\text{Re} = 5000} [\text{ft}^3/\text{min}] \\ Q_{\text{AmpMin}} [\text{ft}^3/\text{min}] \end{array} \right.$$

A0034313

$Q_{Low}$	Effective lower range value
$Q_{min}$	Minimum measurable flow rate
$Q_{Re = 5000}$	Flow rate is dependent on the Reynolds number
$Q_{AmpMin}$	Minimum measurable flow rate based on signal amplitude



The Applicator is available for calculation purposes.

### Upper range value

#### Maximum measurable flow rate based on signal amplitude

The measuring signal amplitude must be below a certain limit value to ensure that the signals can be evaluated without error. This results in a maximum permitted flow rate  $Q_{AmpMax}$ .

Nominal diameter specifications refer to the sensor with the narrowest cross-section.

$$Q_{AmpMax} [m^3/h] = \frac{URV [m/s] \cdot \pi \cdot D_i [m]^2}{4 \cdot \sqrt{\frac{\rho [kg/m^3]}{1 [kg/m^3]}}} \cdot 3600 [s/h]$$

$$Q_{AmpMax} [ft^3/min] = \frac{URV [ft/s] \cdot \pi \cdot D_i [ft]^2}{4 \cdot \sqrt{\frac{\rho [lbm/ft^3]}{0.0624 [lbm/ft^3]}}} \cdot 60 [s/min]$$

A0034316

$Q_{AmpMax}$	Maximum measurable flow rate based on signal amplitude
$D_i$	Internal diameter of measuring tube (corresponds to dimension K → 61)
$\rho$	Density
URV	Limit value for determining the maximum flow rate: <ul style="list-style-type: none"> <li>■ DN 15 to 40: URV = 350</li> <li>■ DN 50 to 300: URV = 600</li> <li>■ NPS ½ to 1½: URV = 1148</li> <li>■ NPS 2 to 12: URV = 1969</li> </ul>

#### Restricted upper range value is dependent on Mach number

For gas applications, an additional restriction applies to the upper range value with regard to the Mach number in the measuring instrument, which must be less than 0.3. The Mach number Ma describes the ratio of the flow velocity v to the sound velocity c in the fluid.

$$Ma = \frac{v [m/s]}{c [m/s]}$$

$$Ma = \frac{v [ft/s]}{c [ft/s]}$$

A0034321

$Ma$	Mach number
$v$	Flow velocity
$c$	Speed of sound

The corresponding flow rate can be derived using the nominal diameter.

$$Q_{Ma=0.3} [\text{m}^3/\text{h}] = \frac{0.3 \cdot c [\text{m/s}] \cdot \pi \cdot D_i [\text{m}]^2}{4} \cdot 3600 [\text{s/h}]$$

$$Q_{Ma=0.3} [\text{ft}^3/\text{min}] = \frac{0.3 \cdot c [\text{ft/s}] \cdot \pi \cdot D_i [\text{ft}]^2}{4} \cdot 60 [\text{s/min}]$$

A0034337

$Q_{Ma=0.3}$  Restricted upper range value is dependent on Mach number

$c$  Speed of sound

$D_i$  Internal diameter of measuring tube (corresponds to dimension  $K \rightarrow$  61)

$\rho$  Density

### Effective upper range value

The effective upper range value  $Q_{\text{High}}$  is determined using the smallest of the three values  $Q_{\text{max}}$ ,  $Q_{\text{AmpMax}}$  and  $Q_{Ma=0.3}$ .

$$Q_{\text{High}} [\text{m}^3/\text{h}] = \min \begin{cases} Q_{\text{max}} [\text{m}^3/\text{h}] \\ Q_{\text{AmpMax}} [\text{m}^3/\text{h}] \\ Q_{Ma=0.3} [\text{m}^3/\text{h}] \end{cases}$$

$$Q_{\text{High}} [\text{ft}^3/\text{min}] = \min \begin{cases} Q_{\text{max}} [\text{ft}^3/\text{min}] \\ Q_{\text{AmpMax}} [\text{ft}^3/\text{min}] \\ Q_{Ma=0.3} [\text{ft}^3/\text{min}] \end{cases}$$

A0034338

$Q_{\text{High}}$  Effective upper range value

$Q_{\text{max}}$  Maximum measurable flow rate

$Q_{\text{AmpMax}}$  Maximum measurable flow rate based on signal amplitude

$Q_{Ma=0.3}$  Restricted upper range value is dependent on Mach number

For liquids, the occurrence of cavitation may also restrict the upper range value.



The Applicator is available for calculation purposes.

### Operable flow range

The value, which is typically up to 49: 1, may vary depending on the operating conditions (ratio between upper range value and lower range value)

### Input signal

#### Current input

Current input	4-20 mA (passive)
Resolution	1 $\mu\text{A}$
Voltage drop	Typically: 2.2 to 3 V for 3.6 to 22 mA
Maximum voltage	$\leq 35 \text{ V}$
Possible input variables	<ul style="list-style-type: none"> <li>■ Pressure</li> <li>■ Temperature</li> <li>■ Density</li> </ul>




### External measured values

To increase the measurement accuracy of certain measured variables or to calculate the corrected volume flow, the automation system can continuously write different measured values to the measuring instrument:

- Operating pressure to increase measurement accuracy (Endress+Hauser recommends the use of a pressure measuring instrument for absolute pressure, e.g. Cerabar M or Cerabar S)
- Medium temperature to increase measurement accuracy (e.g. iTEMP)
- Reference density for calculating the corrected volume flow



- Various pressure measuring devices can be ordered as accessories from Endress+Hauser.
- If using pressure measuring devices, pay attention to outlet runs when installing external devices →  53.

If the measuring instrument does not have pressure or temperature compensation <sup>1)</sup>, it is recommended that external pressure measured values be read in so that the following measured variables can be calculated:

- Energy flow
- Mass flow
- Corrected volume flow

If the device does not have temperature compensation, it is recommended that external pressure measurement values be read in so that the following measured variables can be calculated:

- Energy flow
- Mass flow
- Corrected volume flow


### Integrated pressure and temperature measurement

The measuring device can also directly record external variables for density and energy compensation.

This product version offers the following benefits:

- Measurement of pressure, temperature and flow in a true 2-wire version
- Recording of pressure and temperature at the same point, thus ensuring maximum accuracy of density and energy compensation.
- Continuous monitoring of pressure and temperature, thus enabling complete integration in Heartbeat.
- Easy testing of pressure measurement accuracy:
  - Application of pressure by pressure calibration unit, followed by input into measuring device
  - Automatic error correction performed by device in the event of a deviation
- Availability of calculated line pressure.

### Current input

The measured values are written from the automation system to the measuring device via the current input →  16.

### HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

### Digital communication

The measured values can be written from the automation system to the measuring via:

- FOUNDATION Fieldbus
- PROFIBUS PA
- PROFINET over Ethernet-APL

---

1) Order code for "Sensor version", DSC sensor; measuring tube" option DA, DB



## Output

### Output signal

#### Current output

Current output 1	4-20 mA HART (passive)
Current output 2	4-20 mA (passive)
Resolution	< 1 µA
Damping	Configurable: 0.0 to 999.9 s
Assignable measured variables	<ul style="list-style-type: none"> <li>■ Volume flow</li> <li>■ Corrected volume flow</li> <li>■ Mass flow</li> <li>■ Flow velocity</li> <li>■ Temperature</li> <li>■ Pressure</li> <li>■ Calculated saturated steam pressure</li> <li>■ Total mass flow</li> <li>■ Energy flow</li> <li>■ Heat flow difference</li> </ul>

#### Pulse/frequency/switch output

Function	Can be configured as pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	<ul style="list-style-type: none"> <li>■ DC 35 V</li> <li>■ 50 mA</li> </ul> <p> For information on the Ex connection values →  23</p>
Voltage drop	<ul style="list-style-type: none"> <li>■ For ≤ 2 mA: 2 V</li> <li>■ For 10 mA: 8 V</li> </ul>
Residual current	≤ 0.05 mA
<b>Pulse output</b>	
Pulse width	Configurable: 5 to 2 000 ms
Maximum pulse rate	100 Impulse/s
Pulse value	Configurable
Assignable measured variables	<ul style="list-style-type: none"> <li>■ Mass flow</li> <li>■ Volume flow</li> <li>■ Corrected volume flow</li> <li>■ Total mass flow</li> <li>■ Energy flow</li> <li>■ Heat flow difference</li> </ul>
<b>Frequency output</b>	
Output frequency	Configurable: 0 to 1 000 Hz
Damping	Configurable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	<ul style="list-style-type: none"> <li>■ Volume flow</li> <li>■ Corrected volume flow</li> <li>■ Mass flow</li> <li>■ Flow velocity</li> <li>■ Temperature</li> <li>■ Calculated saturated steam pressure</li> <li>■ Total mass flow</li> <li>■ Energy flow</li> <li>■ Heat flow difference</li> <li>■ Pressure</li> </ul>
<b>Switch output</b>	

<b>Switching behavior</b>	Binary, conductive or non-conductive
<b>Switching delay</b>	Configurable: 0 to 100 s
<b>Number of switching cycles</b>	Unlimited
<b>Assignable functions</b>	<ul style="list-style-type: none"> <li>■ Off</li> <li>■ On</li> <li>■ Diagnostic behavior</li> <li>■ Limit value <ul style="list-style-type: none"> <li>■ Volume flow</li> <li>■ Corrected volume flow</li> <li>■ Mass flow</li> <li>■ Flow velocity</li> <li>■ Temperature</li> <li>■ Calculated saturated steam pressure</li> <li>■ Total mass flow</li> <li>■ Energy flow</li> <li>■ Heat flow difference</li> <li>■ Pressure</li> <li>■ Reynolds number</li> <li>■ Totalizer 1-3</li> </ul> </li> <li>■ Status</li> <li>■ Status of low flow cut off</li> </ul>

**FOUNDATION Fieldbus**

<b>FOUNDATION Fieldbus</b>	H1, IEC 61158-2, galvanically isolated
<b>Data transfer</b>	31.25 kbit/s
<b>Current consumption</b>	15 mA
<b>Permitted supply voltage</b>	9 to 32 V
<b>Bus connection</b>	With integrated reverse polarity protection

**PROFIBUS PA**

<b>PROFIBUS PA</b>	In accordance with EN 50170 Volume 2, IEC 61158-2 (MBP), galvanically isolated
<b>Data transmission</b>	31.25 kbit/s
<b>Current consumption</b>	16 mA
<b>Permitted supply voltage</b>	9 to 32 V
<b>Bus connection</b>	With integrated reverse polarity protection

**PROFINET over Ethernet-APL**

<b>Device use</b>	<b>Device connection to an APL field switch</b> The device may only be operated according to the following APL port classifications: <ul style="list-style-type: none"> <li>■ If used in hazardous areas: SLAA or SLAC <sup>1)</sup></li> <li>■ If used in non-hazardous areas: SLAX</li> <li>■ Connection values of APL field switch (corresponds to APL port classification SPCC or SPAA): <ul style="list-style-type: none"> <li>■ Maximum input voltage: 15 V<sub>DC</sub></li> <li>■ Minimum output values: 0.54 W</li> </ul> </li> </ul> <b>Device connection to an SPE switch</b> If used in non-hazardous areas: suitable SPE switch SPE switch prerequisite: <ul style="list-style-type: none"> <li>■ Support of 10BASE-T1L standard</li> <li>■ Support of PoDL power class 10, 11 or 12</li> <li>■ Detection of SPE field devices without integrated PoDL module</li> </ul> Connection values of SPE switch: <ul style="list-style-type: none"> <li>■ Maximum input voltage: 30 V<sub>DC</sub></li> <li>■ Minimum output values: 1.85 W</li> </ul>
<b>PROFINET</b>	According to IEC 61158 and IEC 61784
<b>Ethernet-APL</b>	According to IEEE 802.3cg, APL port profile specification v1.0, galvanically isolated
<b>Data transfer</b>	10 Mbit/s Full-duplex
<b>Current consumption</b>	<b>Transmitter</b> Max. 55.56 mA
<b>Permitted supply voltage</b>	<ul style="list-style-type: none"> <li>■ Ex: 9 to 15 V</li> <li>■ Non-Ex: 9 to 30 V</li> </ul>
<b>Network connection</b>	With integrated reverse polarity protection

1) For more information on using the device in the hazardous area, see the Ex-specific Safety Instructions

**Signal on alarm**

Depending on the interface, failure information is displayed as follows:

**HART current output**

<b>Device diagnostics</b>	Device condition can be read out via HART Command 48
---------------------------	--

**Current output**

*Current output 4-20 mA*

<b>Failure mode</b>	Choose from: <ul style="list-style-type: none"> <li>■ 4 to 20 mA in accordance with NAMUR recommendation NE 43</li> <li>■ 4 to 20 mA in accordance with US</li> <li>■ Min. value: 3.59 mA</li> <li>■ Max. value: 22.5 mA</li> <li>■ Definable value between: 3.59 to 22.5 mA</li> <li>■ Actual value</li> <li>■ Last valid value</li> </ul>
---------------------	---

**Pulse/frequency/switch output**

<b>Pulse output</b>	
<b>Failure mode</b>	No pulses
<b>Frequency output</b>	

<b>Failure mode</b>	Choose from: <ul style="list-style-type: none"> <li>■ Actual value</li> <li>■ 0 Hz</li> <li>■ Definable value between: 0 to 1 250 Hz</li> </ul>
<b>Switch output</b>	
<b>Failure mode</b>	Choose from: <ul style="list-style-type: none"> <li>■ Current status</li> <li>■ Open</li> <li>■ Closed</li> </ul>

**FOUNDATION Fieldbus**

<b>Status and alarm messages</b>	Diagnostics in accordance with FF-891
<b>Failure current FDE (Fault Disconnection Electronic)</b>	0 mA

**PROFIBUS PA**

<b>Status and alarm messages</b>	Diagnostics in accordance with PROFIBUS PA Profile 3.02
<b>Failure current FDE (Fault Disconnection Electronic)</b>	0 mA

**PROFINET over Ethernet-APL**

<b>Device diagnostics</b>	Diagnostics according to PROFINET PA Profile 4.02
---------------------------	---

**Local display**

<b>Plain text display</b>	With information on cause and remedial measures
<b>Backlight</b>	Additionally for device version with SD03 local display: red lighting indicates a device error.



Status signal as per NAMUR recommendation NE 107

**Interface/protocol**

- Via digital communication:
  - HART protocol
  - FOUNDATION Fieldbus
  - PROFIBUS PA
  - PROFINET over Ethernet-APL
- Via service interface  
Endress+Hauser CDI service interface (Common Data Interface)

<b>Plain text display</b>	With information on cause and remedial measures
---------------------------	---



Additional information on remote operation → 96

### Light emitting diodes (LED)

The LEDs are only available for PROFINET over Ethernet-APL.

<b>Status information</b>	<p>Status indicated by various light emitting diodes</p> <p>The following information is displayed depending on the device version:</p> <ul style="list-style-type: none"> <li>■ Supply voltage active</li> <li>■ Data transmission active</li> <li>■ Network available</li> <li>■ Connection established</li> <li>■ PROFINET blinking feature <sup>1)</sup></li> </ul>
---------------------------	---

1) Only available for PROFINET over Ethernet-APL


### Load

Load for current output: 0 to 500 Ω, depending on the external supply voltage of the power supply unit

#### Calculation of the maximum load

Depending on the supply voltage of the power supply unit ( $U_S$ ), the maximum load ( $R_B$ ) including line resistance must be observed to ensure adequate terminal voltage at the device. In doing so, observe the minimum terminal voltage

- $R_B \leq (U_S - U_{\text{term. min}}) : 0.022 \text{ A}$
- $R_B \leq 500 \Omega$



2 Load for a compact version without local operation

1 Operating range

1.1 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with Ex i and option C "4-20 mA HART + 4-20 mA analog"

1.2 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" for non-hazardous area and Ex d

#### Sample calculation

Supply voltage of power supply unit:

- $U_S = 19 \text{ V}$
- $U_{\text{term. min}} = 12 \text{ V (measuring device)} + 1 \text{ V (local operation without lighting)} = 13 \text{ V}$

Maximum load:  $R_B \leq (19 \text{ V} - 13 \text{ V}) : 0.022 \text{ A} = 273 \Omega$



The minimum terminal voltage ( $U_{\text{kl min}}$ ) increases if local operation is used..

## Ex connection data

## Safety-related values

*Ex d type of protection*

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
Option B	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
Option C	4-20mA HART	$U_{nom} = DC\ 30\ V$ $U_{max} = 250\ V$
	4-20mA analog	
Option D	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
	4 to 20 mA current input	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
Option E	FOUNDATION Fieldbus	$U_{nom} = DC\ 32\ V$ $U_{max} = 250\ V$ $P_{max} = 0.88\ W$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
Option G	PROFIBUS PA	$U_{nom} = DC\ 32\ V$ $U_{max} = 250\ V$ $P_{max} = 0.88\ W$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
Option S	PROFINET over Ethernet-APL/SPE, 10Mbit/s	$U_{nom} = DC\ 17.5\ V$ $U_{max} = 250\ V$ $P_{nom} = 0.9\ W$

1) Internal circuit limited by  $R_i = 760.5\ \Omega$ *Type of protection Ex ec*

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
Option B	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
Option C	4-20mA HART	$U_{nom} = DC\ 30\ V$ $U_{max} = 250\ V$
	4-20mA analog	
Option D	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$

Order code for "Output"	Output type	Safety-related values
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
	4 to 20 mA current input	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
Option E	FOUNDATION Fieldbus	$U_{nom} = DC\ 32\ V$ $U_{max} = 250\ V$ $P_{max} = 0.88\ W$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
Option G	PROFIBUS PA	$U_{nom} = DC\ 32\ V$ $U_{max} = 250\ V$ $P_{max} = 0.88\ W$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
Option S <sup>2)</sup>	PROFINET over Ethernet-APL/SPE, 10Mbit/s	<b>2-WISE power load, APL port profile SLAX</b> $U_{nom} = DC\ 17.5\ V$ $U_{max} = 250\ V$ $P_{nom} = 0.9\ W$

1) Internal circuit limited by  $R_i = 760.5\ \Omega$

2) For installation in systems that are restricted to safe extra-low voltages such as SELV, PELV or ES1. Only one wire is permitted per terminal.

#### Type of protection XP

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
Option B	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
Option C	4-20mA HART	$U_{nom} = DC\ 30\ V$
	4-20mA analog	$U_{max} = 250\ V$
Option D	4-20mA HART	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$
	4 to 20 mA current input	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$
Option E	FOUNDATION Fieldbus	$U_{nom} = DC\ 32\ V$ $U_{max} = 250\ V$ $P_{max} = 0.88\ W$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$



Order code for "Output"	Output type	Safety-related values
Option G	PROFIBUS PA	$U_{nom} = DC\ 32\ V$ $U_{max} = 250\ V$ $P_{max} = 0.88\ W$
	Pulse/frequency/switch output	$U_{nom} = DC\ 35\ V$ $U_{max} = 250\ V$ $P_{max} = 1\ W^{1)}$

1) Internal circuit limited by  $R_i = 760.5\ \Omega$

### Intrinsically safe values

*Ex ia type of protection*

Order code for "Output"	Output type	Intrinsically safe values	
Option A	4-20mA HART	$U_i = DC\ 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 5\ nF$	
Option B	4-20mA HART	$U_i = DC\ 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 5\ nF$	
	Pulse/frequency/switch output	$U_i = DC\ 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 6\ nF$	
Option C	4-20mA HART	$U_i = DC\ 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 30\ nF$	
	4-20mA analog		
Option D	4-20mA HART	$U_i = DC\ 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 5\ nF$	
	Pulse/frequency/switch output	$U_i = DC\ 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 6\ nF$	
	4 to 20 mA current input	$U_i = DC\ 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 5\ nF$	
Option E	FOUNDATION Fieldbus	STANDARD $U_i = 30\ V$ $I_i = 300\ mA$ $P_i = 1.2\ W$ $L_i = 10\ \mu H$ $C_i = 5\ nF$	FISCO $U_i = 17.5\ V$ $I_i = 550\ mA$ $P_i = 5.5\ W$ $L_i = 10\ \mu H$ $C_i = 5\ nF$
	Pulse/frequency/switch output	$U_i = 30\ V$ $I_i = 300\ mA$ $P_i = 1\ W$ $L_i = 0\ \mu H$ $C_i = 6\ nF$	

Order code for "Output"	Output type	Intrinsically safe values	
Option G	PROFIBUS PA	STANDARD $U_i = 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1.2 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$	FISCO $U_i = 17.5 \text{ V}$ $I_i = 550 \text{ mA}$ $P_i = 5.5 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
	Pulse/frequency/switch output	$U_i = 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$	
Option S	PROFINET over Ethernet-APL/SPE, 10Mbit/s	<b>2-WISE power load, APL port profile SLAA<sup>1)</sup></b> <b>Ex ia</b> $U_i = 17.5 \text{ V}$ $I_i = 380 \text{ mA}$ $P_i = 5.32 \text{ W}$ $L_i = \text{negligible}$ $C_i = 1 \text{ nF}$ <b>Cable requirements as per 2-WISE:</b> $R_c = 15 \text{ to } 150 \text{ } \Omega/\text{km}$ $L_c = 0.4 \text{ to } 1 \text{ mH/km}$ $C_c = 45 \text{ to } 200 \text{ nF/km}$ $C_c = C_c \text{ conductor/conductor} + 0.5 \text{ } C_c \text{ conductor/shield}$ if both conductors are potential-free; or $C_c = C_c \text{ conductor/conductor} + C_c \text{ conductor/shield}$ if the shielding is connected to a conductor Length of cable (not including cable stubs): $\leq 200 \text{ m (656.2)}$ Length of cable stubs: $\leq 1 \text{ m (3.3 ft)}$	

1) [Für weitere Optionen siehe Ethernet-APL Installation Drawing HE\\_01622.](#)

#### Type of protection Ex ic

Order code for "Output"	Output type	Intrinsically safe values
Option A	4-20mA HART	$U_i = \text{DC } 35 \text{ V}$ $I_i = \text{n.a.}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
Option B	4-20mA HART	$U_i = \text{DC } 35 \text{ V}$ $I_i = \text{n.a.}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
	Pulse/frequency/switch output	$U_i = \text{DC } 35 \text{ V}$ $I_i = \text{n.a.}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$
Option C	4-20mA HART	$U_i = \text{DC } 30 \text{ V}$ $I_i = \text{n.a.}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 30 \text{ nF}$
	4-20mA analog	

Order code for "Output"	Output type	Intrinsically safe values	
Option D	4-20mA HART	$U_i = \text{DC } 35 \text{ V}$ $I_i = \text{n.a.}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$	
	Pulse/frequency/switch output	$U_i = \text{DC } 35 \text{ V}$ $I_i = \text{n.a.}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$	
	4 to 20 mA current input	$U_i = \text{DC } 35 \text{ V}$ $I_i = \text{n.a.}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$	
Option E	FOUNDATION Fieldbus	STANDARD $U_i = 32 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = \text{n.a.}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$	FISCO $U_i = 17.5 \text{ V}$ $I_i = \text{n.a.}$ $P_i = \text{n.a.}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
	Pulse/frequency/switch output	$U_i = 35 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$	
Option G	PROFIBUS PA	STANDARD $U_i = 32 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = \text{n.a.}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$	FISCO $U_i = 17.5 \text{ V}$ $I_i = \text{n.a.}$ $P_i = \text{n.a.}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
	Pulse/frequency/switch output	$U_i = 35 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$	
Option S	PROFINET over Ethernet-APL/SPE, 10Mbit/s	<b>2-WISE power load, APL port profile SLAC <sup>1)</sup></b> <b>Ex ic</b> $U_i = 17.5 \text{ V}$ $I_i = 380 \text{ mA}$ $P_i = 5.32 \text{ W}$ $L_i = \text{negligible}$ $C_i = 1 \text{ nF}$ <b>Cable requirements as per 2-WISE:</b> $R_c = 15 \text{ to } 150 \text{ } \Omega/\text{km}$ $L_c = 0.4 \text{ to } 1 \text{ mH/km}$ $C_c = 45 \text{ to } 200 \text{ nF/km}$ $C_c = C_c \text{ conductor/conductor} + 0.5 \text{ } C_c \text{ conductor/shield}$ if both conductors are potential-free; or $C_c = C_c \text{ conductor/conductor} + C_c \text{ conductor/shield}$ if the shielding is connected to a conductor Length of cable (not including cable stubs): $\leq 200 \text{ m (656.2)}$ Length of cable stubs: $\leq 1 \text{ m (3.3 ft)}$	

1) [Für weitere Optionen siehe Ethernet-APL Installation Drawing HE\\_01622.](#)

*IS type of protection*

Order code for "Output"	Output type	Intrinsically safe values
Option A	4-20mA HART	$U_i = \text{DC } 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
Option B	4-20mA HART	$U_i = \text{DC } 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
	Pulse/frequency/switch output	$U_i = \text{DC } 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$
Option C	4-20mA HART	$U_i = \text{DC } 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 30 \text{ nF}$
	4-20mA analog	
Option D	4-20mA HART	$U_i = \text{DC } 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
	Pulse/frequency/switch output	$U_i = \text{DC } 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$
	4 to 20 mA current input	$U_i = \text{DC } 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
Option E	FOUNDATION Fieldbus	STANDARD $U_i = 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1.2 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
	Pulse/frequency/switch output	$U_i = 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$
Option G	PROFIBUS PA	STANDARD $U_i = 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1.2 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$

Order code for "Output"	Output type	Intrinsically safe values
	Pulse/frequency/switch output	$U_i = 30 \text{ V}$ $I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \text{ }\mu\text{H}$ $C_i = 6 \text{ nF}$
Option S	PROFINET over Ethernet-APL 10 Mbit/s	$U_i = 17.5 \text{ V}$ $I_i = 380 \text{ mA}$ $P_i = 5.32 \text{ W}$ $C_i = 5 \text{ nF}$ $L_i = 10 \text{ }\mu\text{H}$

**Low flow cut off** The switch points for low flow cut off are preset and can be configured.

**Galvanic isolation** All inputs and outputs are galvanically isolated from one another.


#### Protocol-specific data

##### HART


Manufacturer ID	0x11
Device type ID	0x0038
HART protocol revision	7
Device description files (DTM, DD)	Information and files at: <a href="http://www.endress.com">www.endress.com</a> → Download Area
HART load	<ul style="list-style-type: none"> <li>Min. 250 <math>\Omega</math></li> <li>Max. 500 <math>\Omega</math></li> </ul>
System integration	For information on system integration, see Operating Instructions → 107 <ul style="list-style-type: none"> <li>Measured variables via HART protocol</li> <li>Burst Mode functionality</li> </ul>

##### FOUNDATION Fieldbus

Manufacturer ID	0x452B48
Ident number	0x1038
Device revision	2
DD revision	Information and files at:
CFF revision	<ul style="list-style-type: none"> <li><a href="http://www.endress.com">www.endress.com</a> → Download Area</li> <li><a href="http://www.fieldcommgroup.org">www.fieldcommgroup.org</a></li> </ul>
Device Tester Version (ITK version)	6.2.0
ITK Test Campaign Number	Information: <ul style="list-style-type: none"> <li><a href="http://www.endress.com">www.endress.com</a></li> <li><a href="http://www.fieldcommgroup.org">www.fieldcommgroup.org</a></li> </ul>
Link Master capability (LAS)	Yes
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device
Node address	Factory setting: 247 (0xF7)
Supported functions	The following methods are supported: <ul style="list-style-type: none"> <li>Restart</li> <li>ENP Restart</li> <li>Diagnostic</li> <li>Read events</li> <li>Read trend data</li> </ul>
Virtual Communication Relationships (VCRs)	
Number of VCRs	44

Number of link objects in VFD	50
Permanent entries	1
Client VCRs	0
Server VCRs	10
Source VCRs	43
Sink VCRs	0
Subscriber VCRs	43
Publisher VCRs	43
<b>Device Link Capabilities</b>	
Slot time	4
Min. delay between PDU	8
Max. response delay	Min. 5
System integration	<p>For information on system integration, see Operating Instructions →  107</p> <ul style="list-style-type: none"> <li>▪ Cyclic data transmission</li> <li>▪ Description of the modules</li> <li>▪ Execution times</li> <li>▪ Methods</li> </ul>

### PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x1564
Profile version	3.02
Device description files (GSD, DTM, DD)	<p>Information and files at:</p> <ul style="list-style-type: none"> <li>▪ <a href="http://www.endress.com">www.endress.com</a> → Download Area</li> <li>▪ <a href="https://www.profibus.com">https://www.profibus.com</a></li> </ul>
Supported functions	<ul style="list-style-type: none"> <li>▪ Identification &amp; Maintenance Simple device identification via control system and nameplate</li> <li>▪ PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download</li> <li>▪ Condensed Status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur</li> </ul>
Configuration of the device address	<ul style="list-style-type: none"> <li>▪ DIP switches on the I/O electronics module</li> <li>▪ Local display</li> <li>▪ Via operating tools (e.g. FieldCare)</li> </ul>
System integration	<p>For information on system integration, see Operating Instructions →  107</p> <ul style="list-style-type: none"> <li>▪ Cyclic data transmission</li> <li>▪ Block model</li> <li>▪ Description of the modules</li> </ul>

### PROFINET over Ethernet-APL

Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.43
Communication type	Ethernet Advanced Physical Layer 10BASE-T1L
Conformance Class	Conformance Class B (PA)
Netload Class	PROFINET Netload Robustness Class 2 10 Mbit/s
Data transfer	10 Mbit/s Full-duplex
Cycle times	64 ms


<b>Polarity</b>	Automatic correction of crossed "APL signal +" and "APL signal -" signal lines
<b>Media Redundancy Protocol (MRP)</b>	Not possible (point-to-point connection to APL field switch)
<b>System redundancy support</b>	System redundancy S2 (2 AR with 1 NAP)
<b>Device profile</b>	PROFINET PA profile 4.02 (Application interface identifier API: 0x9700)
<b>Manufacturer ID</b>	17
<b>Device type ID</b>	0xA438
<b>Device description files (GSD, DTM, FDI)</b>	Information and files available at: <ul style="list-style-type: none"> <li>▪ <a href="http://www.endress.com">www.endress.com</a> → Downloads area</li> <li>▪ <a href="http://www.profibus.com">www.profibus.com</a></li> </ul>
<b>Supported connections</b>	<ul style="list-style-type: none"> <li>▪ 2x AR (IO Controller AR)</li> <li>▪ 2x AR (IO Supervisor Device AR connection allowed)</li> </ul>
<b>Configuration options for measuring instrument</b>	<ul style="list-style-type: none"> <li>▪ Asset management software (FieldCare, DeviceCare, Field Xpert)</li> <li>▪ Integrated Web server via Web browser and IP address</li> <li>▪ Device master file (GSD), can be read out via the integrated Web server of the measuring instrument.</li> <li>▪ Onsite operation</li> </ul>
<b>Configuration of the device name</b>	<ul style="list-style-type: none"> <li>▪ DCP protocol</li> <li>▪ Asset management software (FieldCare, DeviceCare, Field Xpert)</li> <li>▪ Integrated web server</li> </ul>
<b>Supported functions</b>	<ul style="list-style-type: none"> <li>▪ Identification &amp; Maintenance, simple device identifier via: <ul style="list-style-type: none"> <li>▪ Control system</li> <li>▪ Nameplate</li> </ul> </li> <li>▪ Measured value status The process variables are communicated with a measured value status</li> <li>▪ Blinking feature via the local display for simple device identification and assignment</li> <li>▪ Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM with FDI package)</li> </ul>
<b>System integration</b>	Information regarding system integration: Operating Instructions . <ul style="list-style-type: none"> <li>▪ Cyclic data transmission</li> <li>▪ Overview and description of the modules</li> <li>▪ Status coding</li> <li>▪ Factory setting</li> </ul>

## Power supply

### Terminal assignment

### Transmitter

#### Connection versions

	
<p>Maximum number of terminals Terminals 1 to 6: Without integrated overvoltage protection</p>	<p>Maximum number of terminals for order code for "Accessory mounted", option NA "Overvoltage protection"</p> <ul style="list-style-type: none"> <li>Terminals 1 to 4: With integrated overvoltage protection</li> <li>Terminals 5 to 6: Without integrated overvoltage protection</li> </ul>
<p>1 Output 1 (passive): supply voltage and signal transmission  2 Output 2 (passive): supply voltage and signal transmission  3 Input (passive): supply voltage and signal transmission  4 Ground terminal for cable shield</p>	

Order code for "Output"	Terminal numbers					
	Output 1		Output 2		Input	
	1 (+)	2 (-)	3 (+)	4 (-)	5 (+)	6 (-)
Option A	4-20 mA HART (passive)		-		-	
Option B <sup>1)</sup>	4-20 mA HART (passive)		Pulse/frequency/switch output (passive)		-	
Option C <sup>1)</sup>	4-20 mA HART (passive)		4-20 mA analog (passive)		-	
Option D <sup>1) 2)</sup>	4-20 mA HART (passive)		Pulse/frequency/switch output (passive)		4-20 mA current input (passive)	
Option E <sup>1) 3)</sup>	FOUNDATION Fieldbus		Pulse/frequency/switch output (passive)		-	
Option G <sup>1) 4)</sup>	PROFIBUS PA		Pulse/frequency/switch output (passive)		-	
Option S <sup>1) 5)</sup>	PROFINET over Ethernet-APL/SPE, 10 Mbit/s		-		-	

- 1) Output 1 must always be used; output 2 is optional.
- 2) The integrated overvoltage protection is not used with option D: Terminals 5 and 6 (current input) are not protected against overvoltage.
- 3) FOUNDATION Fieldbus with integrated reverse polarity protection.
- 4) PROFIBUS PA with integrated reverse polarity protection.
- 5) PROFINET over Ethernet-APL with integrated reverse polarity protection.



## Connecting cable for remote version

### Transmitter and sensor connection housing

In the case of the remote version, the sensor and transmitter are mounted separately from on another and connected by a connecting cable. Connection is performed via the sensor connection housing and the transmitter housing.

**i** How the connecting cable is connected in the transmitter housing depends on the measuring instrument approval and the version of the connecting cable used.

In the following versions, only terminals can be used for connection in the transmitter housing:


- Order code for "Electrical connection", option B, C, D, 6
- Certain approvals: Ex nA, Ex ec, Ex tb and Division 1
- Use of reinforced connecting cable
- Order code for "Sensor version; DSC sensor; measuring tube", option DA, DB

In the following versions, an M12 device connector is used for connection in the transmitter housing:

- All other approvals
- Use of connecting cable (standard)

Terminals are always used to connect the connecting cable in the sensor connection housing (tightening torques for screws for cable strain relief: 1.2 to 1.7 Nm).

### Connection via terminals







A0041608

1. Loosen the securing clamp of the transmitter housing.
2. Turn the transmitter housing clockwise by approx. 20°.
3. **NOTICE**


**The connection board of the wall housing is connected to the electronics board of the transmitter via a signal cable!**


- Pay attention to the signal cable when lifting the transmitter housing!

Lift the transmitter housing, plug the signal cable out of the connection board of the wall holder and remove the transmitter housing.

4. Release the cable gland and insert the connecting cable (use the shorter stripped end of the connecting cable).
5. Wire the connecting cable →  3,  34 →  4,  34.
6. Reverse the removal procedure to reassemble the transmitter housing.
7. Firmly tighten the cable gland.

Connecting cable (standard, reinforced)




 3 Terminals for connection compartment in the transmitter wall holder and the sensor connection housing


- 1 Terminals for connecting cable  
2 Grounding via the cable strain relief

Terminal number	Assignment	Cable color Connecting cable
1	Supply voltage	Brown
2	Grounding	White
3	RS485 (+)	Yellow
4	RS485 (-)	Green

Connecting cable (option "mass pressure-/temperature-compensated")

Order code for "Sensor version; DSC sensor; measuring tube", option DA, DB




 4 Terminals for connection compartment in the transmitter wall holder and the sensor connection housing

- 1 Terminals for connecting cable  
2 Grounding via the cable strain relief

Terminal number	Assignment	Cable color Connecting cable
1	RS485 (-) DPC	Brown
2	RS485 (+) DPC	White
3	Reset	Green
4	Supply voltage	Red
5	Grounding	Black
6	RS485 (+)	Yellow
7	RS485 (-)	Blue

Pin assignment, device plug

PROFIBUS PA


	Pin	Assignment		Coding	Plug/socket
	1	+	PROFIBUS PA +	A	Plug
	2		Grounding		
	3	-	PROFIBUS PA -		
	4		Not used		




Recommended plug:

- Binder, series 713, part no. 99 1430 814 04
- Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

FOUNDATION Fieldbus

	Pin	Assignment		Coding	Plug/socket
	1	+	Signal +	A	Plug
	2	-	Signal -		
	3		Grounding		
	4		Not used		

PROFINET over Ethernet-APL

	Pin	Assignment	Coding	Plug/socket
	1	APL signal -	A	Socket
	2	APL signal +		
	3	Cable shield <sup>1</sup>		
	4	Not used		
	Metal plug housing	Cable shield		
<sup>1</sup> If a cable shield is used				



Recommended plug:

- Binder, series 713, part no. 99 1430 814 04
- Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

Supply voltage

Transmitter

An external power supply is required for each output.

*Supply voltage for a compact version without a local display <sup>1)</sup>*

Order code for "Output; input"	Minimum Terminal voltage <sup>2)</sup>	Maximum Terminal voltage
Option <b>A</b> : 4-20 mA HART	≥ DC 12 V	DC 35 V
Option <b>B</b> : 4-20 mA HART, pulse/frequency/switch output	≥ DC 12 V	DC 35 V
Option <b>C</b> : 4-20 mA HART + 4-20 mA analog	≥ DC 12 V	DC 30 V
Option <b>D</b> : 4-20 mA HART, pulse/frequency/switch output, 4-20 mA current input <sup>3)</sup>	≥ DC 12 V	DC 35 V
Option <b>E</b> : FOUNDATION Fieldbus, pulse/frequency/switch output	≥ DC 9 V	DC 32 V
Option <b>G</b> : PROFIBUS PA, pulse/frequency/switch output	≥ DC 9 V	DC 32 V
Option <b>S</b> : PROFINET over Ethernet-APL/SPE, 10 Mbit/s	≥ DC 9 V	DC 15 V

- 1) In event of external supply voltage of the power supply unit with load, the PROFIBUS DP/PA coupler or FOUNDATION Fieldbus power conditioner  
2) Increase of minimum terminal voltage with local operation: See the table below.  
3) Voltage drop 2.2 to 3 V for 3.59 to 22 mA

*Increase of minimum terminal voltage with local operation*

Order code for "Display; operation"	Increase in minimum Terminal voltage
Option <b>C</b> : Local operation SD02	+ DC 1 V
Option <b>E</b> : Local operation SD03 with lighting ( <b>backlighting</b> not used)	+ DC 1 V
Option <b>E</b> : Local operation SD03 with lighting ( <b>backlighting</b> used)	+ DC 3 V

Order code for "Sensor version; DSC sensor; measuring tube"	Increase in minimum Terminal voltage
Option <b>DA</b> : Mass steam; 316L; 316L (integrated pressure/temperature measurement)	+ DC 1 V
Option <b>DB</b> : Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement)	+ DC 1 V



- For information on the load, see → 22
- Available as accessory: Power supply unit for power supply → 107
- For information on the Ex connection values → 23

**Power consumption****Transmitter**

Order code for "Output; input"	Maximum power consumption
Option A: 4-20 mA HART	770 mW
Option B: 4-20 mA HART, pulse/frequency/switch output	<ul style="list-style-type: none"> <li>Operation with output 1: 770 mW</li> <li>Operation with output 1 and 2: 2 770 mW</li> </ul>

Order code for "Output; input"	Maximum power consumption
Option C: 4-20 mA HART + 4-20 mA analog	<ul style="list-style-type: none"> <li>■ Operation with output 1: 660 mW</li> <li>■ Operation with output 1 and 2: 1 320 mW</li> </ul>
Option D: 4-20 mA HART, pulse/frequency/switch output, 4-20 mA current input	<ul style="list-style-type: none"> <li>■ Operation with output 1: 770 mW</li> <li>■ Operation with output 1 and 2: 2770 mW</li> <li>■ Operation with output 1 and input: 840 mW</li> <li>■ Operation with output 1, 2 and input: 2840 mW</li> </ul>
Option E: FOUNDATION Fieldbus, pulse/frequency/switch output	<ul style="list-style-type: none"> <li>■ Operation with output 1: 512 mW</li> <li>■ Operation with output 1 and 2: 2 512 mW</li> </ul>
Option G: PROFIBUS PA, pulse/frequency/switch output	<ul style="list-style-type: none"> <li>■ Operation with output 1: 512 mW</li> <li>■ Operation with output 1 and 2: 2 512 mW</li> </ul>
Option S: PROFINET over Ethernet-APL/SPE, 10 Mbit/s	Operation with output 1: Ex: 833 mW Non-Ex: 1.5 W



For information on the Ex connection values → 23

## Current consumption

### Current output

For every 4-20 mA current output or current output: 3.6 to 22.5 mA



If the option **Defined value** is selected in the **Failure mode** parameter : 3.59 to 22.5 mA

### Current input

3.59 to 22.5 mA



Internal current limiting: max. 26 mA

### FOUNDATION Fieldbus

15 mA

### PROFIBUS PA


15 mA

### PROFINET over Ethernet-APL

20 to 55.56 mA


## Power supply failure

- Totalizers stop at the last value measured.
- Depending on the device version, the configuration is retained in the device memory or in the pluggable data memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

**Electrical connection****Transmitter connection**

A0033480

1 Cable entries for inputs/outputs

**Remote version connection***Connecting cable*


A0033481

 5 *Connecting cable connection*

1 Wall holder with connection compartment (transmitter)

2 Connecting cable

3 Sensor connection housing

 How the connecting cable is connected in the transmitter housing depends on the measuring instrument approval and the version of the connecting cable used.

In the following versions, only terminals can be used for connection in the transmitter housing:

- Order code for "Electrical connection", option B, C, D, 6
- Certain approvals: Ex nA, Ex ec, Ex tb and Division 1
- Use of reinforced connecting cable
- Order code for "Sensor version; DSC sensor; measuring tube", option DA, DB


In the following versions, an M12 device connector is used for connection in the transmitter housing:

- All other approvals
- Use of connecting cable (standard)

Terminals are always used to connect the connecting cable in the sensor connection housing (tightening torques for screws for cable strain relief: 1.2 to 1.7 Nm).

## Connection examples

### Current output 4 to 20 mA (without HART)




A0055852

6 Connection example for 4 to 20 mA current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Optional additional display unit: Observe maximum load
- 4 Transmitter with current output (passive)

### Current input 4 to 20 mA




A0055853

7 Connection example for 4 to 20 mA current input

- 1 Power supply
- 2 External measuring instrument with 4 to 20 mA passive current output. e.g. pressure or temperature
- 3 Transmitter with 4 to 20 mA current input

### Pulse output/frequency output/switch output




A0055855

8 Connection example for pulse output/frequency output/switch output (passive)

- 1 Automation system with pulse input/frequency input/switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter with pulse output/frequency output/switch output (passive)

## Current output 4 to 20 mA HART



A0055861


9 Connection example for 4 to 20 mA current output with HART (passive)

- 1 Automation system with 4 to 20 mA current input with HART (e.g. PLC)
- 2 Power supply
- 3 Optional display unit: Note maximum load
- 4 Transmitter with 4 to 20 mA current output with HART (passive)
- 5 Ground cable shield at one end. For installations in compliance with NAMUR NE 89, grounding of the cable shield on both sides is required.

## PROFIBUS PA

See <https://www.profibus.com> "PROFIBUS Installation Guidelines".

## FOUNDATION Fieldbus



A0028768






10 Connection example for FOUNDATION Fieldbus

- 1 Automation system (e.g. PLC)
- 2 Power Conditioner (FOUNDATION Fieldbus)
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring instrument
- 6 Local grounding
- 7 Bus terminator
- 8 Potential equalization conductor

## Ethernet-APL

See <https://www.profibus.com> Ethernet-APL White Paper "



<b>Potential equalization</b>	<b>Requirements</b> For potential equalization: <ul style="list-style-type: none"> <li>■ Pay attention to in-house grounding concepts</li> <li>■ Take account of operating conditions, such as the pipe material and grounding</li> <li>■ Connect the medium, sensor and transmitter to the same electric potential</li> <li>■ Use a ground cable with a minimum cross-section of 6 mm<sup>2</sup> (10 AWG) and a cable lug for potential equalization connections</li> </ul>
<b>Terminals</b>	<ul style="list-style-type: none"> <li>■ For device version without integrated overvoltage protection: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm<sup>2</sup> (20 to 14 AWG)</li> <li>■ For device version with integrated overvoltage protection: screw terminals for wire cross-sections 0.2 to 2.5 mm<sup>2</sup> (24 to 14 AWG)</li> </ul>
<b>Cable entries</b>	 The type of cable entry available depends on the specific device version.  <b>Cable gland (not for Ex d)</b> M20 × 1.5  <b>Thread for cable entry</b> <ul style="list-style-type: none"> <li>■ NPT ½"</li> <li>■ G ½"</li> <li>■ M20 × 1.5</li> </ul>
<b>Cable specification</b>	<b>Permitted temperature range</b> <ul style="list-style-type: none"> <li>■ The installation guidelines that apply in the country of installation must be observed.</li> <li>■ The cables must be suitable for the minimum and maximum temperatures to be expected.</li> </ul> <b>Signal cable</b>  <i>4 to 20 mA current output (without HART)</i> Standard installation cable is sufficient.  <i>Pulse/frequency/switch output</i> Standard installation cable is sufficient.  <i>Current output 4 to 20 mA HART</i> Shielded twisted-pair cable.  See <a href="https://www.fieldcommgroup.org">https://www.fieldcommgroup.org</a> "HART PROTOCOL SPECIFICATIONS".  <i>PROFIBUS PA</i> Shielded twisted-pair cable. Cable type A is recommended.  See <a href="https://www.profibus.com">https://www.profibus.com</a> "PROFIBUS Installation Guidelines".  <i>Ethernet-APL</i> Shielded twisted-pair cable. Cable type A is recommended.  See <a href="https://www.profibus.com">https://www.profibus.com</a> Ethernet-APL White Paper "  <i>FOUNDATION Fieldbus</i> Twisted, shielded two-wire cable.  For further information on planning and installing FOUNDATION Fieldbus networks see: <ul style="list-style-type: none"> <li>■ Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)</li> <li>■ FOUNDATION Fieldbus Guideline</li> <li>■ IEC 61158-2 (MBP)</li> </ul>

**Connecting cable for remote version***Connecting cable (standard)*

<b>Standard cable</b>	2 × 2 × 0.5 mm <sup>2</sup> (22 AWG) PVC cable with common shield (2 pairs, pair-stranded) <sup>1)</sup>
<b>Flame resistance</b>	According to DIN EN 60332-1-2
<b>Oil resistance</b>	According to DIN EN 60811-2-1
<b>Shielding</b>	Galvanized copper-braid, opt. density approx. 85 %
<b>Cable length</b>	5 m (15 ft), 10 m (30 ft), 20 m (60 ft), 30 m (90 ft)
<b>Continuous operating temperature</b>	When mounted in a fixed position: -50 to +105 °C (-58 to +221 °F); when cable can move freely: -25 to +105 °C (-13 to +221 °F)

- 1) UV radiation may cause damage to the outer jacket of the cable. Protect the cable from exposure to sun as much as possible.

*Connecting cable (armored)*

<b>Cable, armored</b>	2 × 2 × 0.34 mm <sup>2</sup> (22 AWG) PVC cable with common shield (2 pairs, pair-stranded) and additional steel-wire braided sheath <sup>1)</sup>
<b>Flame resistance</b>	According to DIN EN 60332-1-2
<b>Oil resistance</b>	According to DIN EN 60811-2-1
<b>Shielding</b>	Galvanized copper-braid, opt. density approx. 85%
<b>Strain relief and reinforcement</b>	Steel-wire braid, galvanized
<b>Cable length</b>	10 m (30 ft), 20 m (60 ft), 30 m (90 ft)
<b>Continuous operating temperature</b>	When mounted in a fixed position: -50 to +105 °C (-58 to +221 °F); when cable can move freely: -25 to +105 °C (-13 to +221 °F)

- 1) UV radiation may cause damage to the outer jacket of the cable. Protect the cable from exposure to sun as much as possible.

*Connecting cable (option "mass pressure-/temperature-compensated")*

Order code for "Sensor version; DSC sensor; measuring tube", option DA, DB

<b>Standard cable</b>	[(3 × 2) + 1] × 0.34 mm <sup>2</sup> (22 AWG) PVC cable with common shield (3 pairs, pair-stranded) <sup>1)</sup>
<b>Flame resistance</b>	According to DIN EN 60332-1-2
<b>Oil resistance</b>	According to DIN EN 60811-2-1
<b>Shielding</b>	Galvanized copper-braid, opt. density approx. 85%
<b>Cable length</b>	10 m (30 ft), 30 m (90 ft)
<b>Continuous operating temperature</b>	When mounted in a fixed position: -50 to +105 °C (-58 to +221 °F); when cable can move freely: -25 to +105 °C (-13 to +221 °F)

- 1) UV radiation may cause damage to the outer jacket of the cable. Protect the cable from exposure to sun as much as possible.

**Connecting cable (option "mass pressure-/temperature-compensated")**


Order code for "Sensor version; DSC sensor; measuring tube", option DA, DB

Standard cable	$[(3 \times 2) + 1] \times 0.34 \text{ mm}^2$ (22 AWG) PVC cable with common shield (3 pairs, pair-stranded) <sup>1)</sup>
Flame resistance	According to DIN EN 60332-1-2
Oil resistance	According to DIN EN 60811-2-1
Shielding	Galvanized copper-braid, opt. density approx. 85%
Cable length	10 m (30 ft), 30 m (90 ft)
Continuous operating temperature	When mounted in a fixed position: -50 to +105 °C (-58 to +221 °F); when cable can move freely: -25 to +105 °C (-13 to +221 °F)



- 1) UV radiation may cause damage to the outer jacket of the cable. Protect the cable from exposure to sun as much as possible.

Overvoltage protection

The device can be ordered with integrated overvoltage protection:  
*Order code for "Accessory mounted", option NA "Overvoltage protection"*

Input voltage range	Values correspond to supply voltage specifications →  35 <sup>1)</sup>
Resistance per channel	$2 \cdot 0.5 \Omega$ max.
DC sparkover voltage	400 to 700 V
Trip surge voltage	< 800 V
Capacitance at 1 MHz	< 1.5 pF
Nominal discharge current (8/20 µs)	10 kA
Temperature range	-40 to +85 °C (-40 to +185 °F)

- 1) The voltage is reduced by the amount of the internal resistance  $I_{\min} \cdot R_i$


-  Depending on the temperature class, restrictions apply to the ambient temperature for device versions with overvoltage protection .
-  For detailed information on the temperature tables, see the "Safety Instructions" (XA) for the device.

The use of an external overvoltage protection, e.g. HAW 569, is recommended.

Performance characteristics


Reference operating conditions

- Error limits following ISO/DIN 11631
- +20 to +30 °C (+68 to +86 °F)
- 2 to 4 bar (29 to 58 psi)
- Calibration system traceable to national standards
- Calibration with the process connection corresponding to the particular standard


-  To obtain measured errors, use the *Applicator* sizing tool →  106

Maximum measurement error

Base accuracy  
o.r. = of reading



A0034077

Reynolds number	
Re <sub>1</sub>	5 000
Re <sub>2</sub>	10 000
Re <sub>min</sub>	Reynolds number for minimum permitted volume flow in measuring tube <ul style="list-style-type: none"> <li>■ Standard</li> <li>■ Option N "0.65% volume PremiumCal 5-point"</li> </ul>
	$Q_{\text{AmpMin}} [\text{m}^3/\text{h}] = \frac{v_{\text{AmpMin}} [\text{m/s}] \cdot \pi \cdot (D_i [\text{m}])^2}{4} \cdot 3600 [\text{s/h}]$ $Q_{\text{AmpMin}} [\text{ft}^3/\text{min}] = \frac{v_{\text{AmpMin}} [\text{ft/s}] \cdot \pi \cdot (D_i [\text{ft}])^2}{4} \cdot 60 [\text{s/min}]$
Re <sub>max</sub>	Defined by internal diameter of measuring tube, Mach number and maximum permitted velocity in measuring tube $Re_{\text{max}} = \frac{\rho \cdot 4 \cdot Q_{\text{Heigh}}}{\mu \cdot K}$
	 Further information on effective upper range value Q <sub>High</sub> → 15

A0034304

A0034339

### Volume flow

Medium type		Incompressible		Compressible	
Reynolds number Range	Measurement error	PremiumCal <sup>1)</sup>	Standard	PremiumCal <sup>1)</sup>	Standard
Re <sub>2</sub> to Re <sub>max</sub>	A1	< 0.65 %	< 0.75 %	< 0.9 %	< 1.0 %
Re <sub>1</sub> to Re <sub>2</sub>	A2	< 2.5 %	< 5.0 %	< 2.5 %	< 5.0 %

1) Order code for "Calibration flow", option N "0.65% volume PremiumCal 5-point"

### Temperature

- Saturated steam and liquids at room temperature, if T > 100 °C (212 °F):  
< 1 °C (1.8 °F)
- Gas: < 1 % o.r. [K]
- Rise time 50 % (stirred under water, following IEC 60751): 8 s

*Pressure*

Order code for "Pressure component" <sup>1)</sup>	Nominal value [bar abs.]	Pressure ranges and measured errors <sup>2)</sup>	
		Pressure range [bar abs.]	Measurement error
Option <b>B</b> Pressure measuring cell 2 bar_a	2	$0.01 \leq p \leq 0.4$ $0.4 \leq p \leq 2$	0.5 % of 0.4 bar abs. 0.5 % o.r.
Option <b>C</b> Pressure measuring cell 4 bar_a	4	$0.01 \leq p \leq 0.8$ $0.8 \leq p \leq 4$	0.5 % of 0.8 bar abs. 0.5 % o.r.
Option <b>D</b> Pressure measuring cell 10 bar_a	10	$0.01 \leq p \leq 2$ $2 \leq p \leq 10$	0.5 % of 2 bar abs. 0.5 % o.r.
Option <b>E</b> Pressure measuring cell 40 bar_a	40	$0.01 \leq p \leq 8$ $8 \leq p \leq 40$	0.5 % of 8 bar abs. 0.5 % o.r.

- 1) Sensor version "Mass (integrated pressure/temperature measurement)" is only available for measuring instruments in the HART, PROFINET over Ethernet-APL communication modes.
- 2) The specific measured errors refer to the position of the measurement in the measuring tube and do not correspond to the pressure in the pipe connection line upstream or downstream from the measuring instrument. No measured error is specified for the measured error for the "pressure" measured variable that can be assigned to the outputs.

*Mass flow saturated steam*

Sensor version				Mass (integrated temperature measurement) <sup>1)</sup>		Mass (integrated pressure/temperature measurement) <sup>2) 1)</sup>	
Process pressure [bar abs.]	Flow velocity [m/s (ft/s)]	Reynolds number Range	Measurement error	PremiumCal <sup>3)</sup>	Standard	PremiumCal <sup>3)</sup>	Standard
> 4.76	20 to 50 (66 to 164)	Re <sub>2</sub> to Re <sub>max</sub>	A1	< 1.6 %	< 1.7 %	< 1.4 %	< 1.5 %
> 3.62	10 to 70 (33 to 230)	Re <sub>2</sub> to Re <sub>max</sub>	A1	< 1.9 %	< 2.0 %	< 1.7 %	< 1.8 %
In all cases not specified here, the following applies: < 5.7 %							

- 1) Detailed calculation with Applicator
- 2) Sensor version only available for measuring instruments in the HART, PROFINET over Ethernet-APL communication modes.
- 3) Order code for "Calibration flow", option N "0.65% volume PremiumCal 5-point"

*Mass flow of superheated steam/gases<sup>2) 3)</sup>*

Sensor version				Mass (integrated pressure/temperature measurement) <sup>1) 2)</sup>		Mass (integrated temperature measurement) + external pressure compensation <sup>3) 2)</sup>	
Process pressure [bar abs.]	Flow velocity [m/s (ft/s)]	Reynolds number Range	Measurement error	PremiumCal <sup>4)</sup>	Standard	PremiumCal <sup>4)</sup>	Standard
< 40	All velocities	Re <sub>2</sub> to Re <sub>max</sub>	A1	< 1.4 %	< 1.5 %	< 1.6 %	< 1.7 %
< 120		Re <sub>2</sub> to Re <sub>max</sub>	A1	< 2.3 %	< 2.4 %	< 2.5 %	< 2.6 %
In all cases not specified here, the following applies: < 6.6 %							

- 1) Sensor version only available for measuring instruments in the HART, PROFINET over Ethernet-APL communication modes
- 2) Detailed calculation with Applicator
- 3) The use of a Cerabar S is required for the measurement errors listed in the following section. The measurement error used to calculate the error in the measured pressure is 0.15 %.
- 4) Order code for "Calibration flow", option N "0.65% volume PremiumCal 5-point"

*Water mass flow*

Sensor version				Mass (integrated temperature measurement)	
Process pressure [bar abs.]	Flow velocity [m/s (ft/s)]	Reynolds number range	Measured value deviation	PremiumCal <sup>1)</sup>	Standard
All pressures	All velocities	Re <sub>2</sub> to Re <sub>max</sub>	A1	< 0.75 %	< 0.85 %
		Re <sub>1</sub> to Re <sub>2</sub>	A2	< 2.6 %	< 2.7 %

- 1) Order code for "Calibration flow", option N "0.65% volume PremiumCal 5-point"

*Mass flow (user-specific liquids)*

To specify the system accuracy, Endress+Hauser requires information about the type of liquid and its operating temperature or information in table form about the dependency between the liquid density and the temperature.

*Example*

- Acetone is to be measured at fluid temperatures from +70 to +90 °C (+158 to +194 °F).
- For this purpose, the **Reference temperature** parameter (7703) (here 80 °C (176 °F)), **Reference density** parameter (7700) (here 720.00 kg/m<sup>3</sup>) and **Linear expansion coefficient** parameter (7621) (here  $18.0298 \times 10^{-4} \text{ 1/}^\circ\text{C}$ ) must be entered in the transmitter.
- The overall system uncertainty, which is less than 0.9 % for the example above, is comprised of the following measurement uncertainties: uncertainty of volume flow measurement, uncertainty of temperature measurement, uncertainty of the density-temperature correlation used (including the resulting uncertainty of density).

*Mass flow (other media)*

Depends on the selected fluid and the pressure value, which is specified in the parameters. Individual error analysis must be performed.

**Diameter mismatch correction**

The measuring device is calibrated according to the ordered process connection. This calibration takes account of the edge at the transition from the mating pipe to the process connection. If the mating pipe used deviates from the ordered process connection, a diameter mismatch correction can compensate for the effects. The difference between the internal diameter of the ordered process connection and the internal diameter of the mating pipe used must be taken into consideration.

- 2) Single gas, gas mixture, air: NEL40; natural gas: ISO 12213-2 contains AGA8-DC92, AGA NX-19, ISO 12213-3 contains SGERG-88 and AGA8 Gross Method 1
- 3) The measuring instrument is calibrated with water and has been verified under pressure on gas calibration rigs.

The measuring device can correct shifts in the calibration factor which are caused, for example, by a diameter mismatch between the device flange (e.g. ASME B16.5/Sch. 80, DN 50 (2")) and the mating pipe (e.g. ASME B16.5/Sch. 40, DN 50 (2")). Only apply diameter mismatch correction within the following limit values (listed below) for which test measurements have also been performed.

**Flange connection:**

- DN 15 (½"): ±20 % of the internal diameter
- DN 25 (1"): ±15 % of the internal diameter
- DN 40 (1½"): ±12 % of the internal diameter
- DN ≥ 50 (2"): ±10 % of the internal diameter

If the standard internal diameter of the ordered process connection differs from the internal diameter of the mating pipe, an additional measuring uncertainty of approx. 2 % o.r. must be expected.

**Example**

Influence of the diameter mismatch without using the correction function:

- Mating pipe DN 100 (4"), Schedule 80
- Device flange DN 100 (4"), Schedule 40
- This installation position results in a diameter mismatch of 5 mm (0.2 in). If the correction function is not used, an additional measuring uncertainty of approx. 2 % o.r. must be expected.
- If the basic conditions are met and the feature is enabled, the additional measuring uncertainty is 1 % o.r.



For detailed information on the parameters for diameter mismatch correction, see the Operating Instructions → 107

**Accuracy of outputs**

The outputs have the following base accuracy specifications.

*Current output*

Accuracy	±10 µA
----------	--------

*Pulse/frequency output*

o.r. = of reading


Accuracy	Max. ±100 ppm o.r.
----------	--------------------

**Repeatability**

o.r. = of reading

$$r = \left\{ \frac{100 \cdot D_i^3}{V} \right\}^{1/2} \% \text{ o.r.}$$

A0042121-EN



A0042123-EN

11 Repeatability = 0.1 % o.r. with a measured volume  $[m^3]$  of  $V = 10\,000 \cdot D_i^3$

The repeatability can be improved if the measured volume is increased. Repeatability is not a device characteristic but a statistical variable that is dependent on the boundary conditions indicated.

#### Response time

If all the configurable functions for filter times (flow damping, display damping, current output time constant, frequency output time constant, status output time constant) are set to 0, in the event of vortex frequencies of 10 Hz and higher a response time of  $\max(T_v, 100 \text{ ms})$  can be expected.

In the event of measuring frequencies  $< 10 \text{ Hz}$ , the response time is  $> 100 \text{ ms}$  and can be up to 10 s.  $T_v$  is the average vortex period duration of the flowing fluid.

#### Relative humidity

The device is suitable for use in outdoor and indoor areas with a relative humidity of 5 to 95%.

#### Operating height

According to EN 61010-1

- $\leq 2\,000 \text{ m}$  (6 562 ft)
- $> 2\,000 \text{ m}$  (6 562 ft) with additional overvoltage protection (e.g. Endress+Hauser HAW Series)

#### Influence of ambient temperature

##### Current output

o.r. = of reading

Additional error, in relation to the span of 16 mA:

Temperature coefficient at zero point (4 mA)	0.02 %/10 K
Temperature coefficient with span (20 mA)	0.05 %/10 K

##### Pulse/frequency output


o.r. = of reading

Temperature coefficient	Max. $\pm 100 \text{ ppm o.r.}$
-------------------------	---------------------------------



# Installation

## Mounting location





- 1    Installation suitable for gases and steam  
2    Installation not suitable for liquids

## Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

Vortex meters require a fully developed flow profile as a prerequisite for correct volume flow measurement. Therefore, please note the following:

Orientation			Recommendation	
			Compact version	Remote version
A	Vertical orientation (liquids)		✓✓ <sup>1)</sup>	✓✓
A	Vertical orientation (dry gases)		✓✓	✓✓
B	Horizontal orientation, transmitter head up		✓✓ <sup>2)</sup>	✓✓





Orientation			Recommendation	
			Compact version	Remote version
<b>C</b>	Horizontal orientation, transmitter head down	 A0015590	✓✓ <sup>3)</sup>	✓✓
<b>D</b>	Horizontal orientation, transmitter head at side	 A0015592	✓✓	✓✓

- 1) In the case of liquids, there should be upward flow in vertical pipes to avoid partial pipe filling (Fig. A). Disruption in flow measurement!
- 2) In the case of hot media (e.g. steam or medium temperature (TM)  $\geq 200$  °C (392 °F)): orientation C or D
- 3) In the case of very cold media (e.g. liquid nitrogen): orientation B or D

**i** For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:

- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.

#### Pressure measuring cell

Steam pressure measurement			Option DA
<b>E</b>	<ul style="list-style-type: none"> <li>▪ With the transmitter installed at the bottom or at the side</li> <li>▪ Protection against rising heat</li> </ul>	 A0034057	✓✓
<b>F</b>	<ul style="list-style-type: none"> <li>▪ Reduction in temperature to almost ambient temperature due to siphon<sup>1)</sup></li> </ul>	 A0034058	✓✓
Gas pressure measurement			Option DB
<b>G</b>	<ul style="list-style-type: none"> <li>▪ Pressure measuring cell with shutoff device above tapping point</li> <li>▪ Discharge of any condensate into the process</li> </ul>	 A0034092	✓✓
Liquid pressure measurement			Option DB
<b>H</b>	Device with shutoff device at the same level as tapping point	 A0034091	✓✓


- 1) Note max. permitted ambient temperature of transmitter → 55.

### Minimum spacing and cable length

Order code for "Sensor version", option "Mass" DA, DB

**i** For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:

- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.



*A* Minimum spacing in all directions


*L* Required cable length

The following dimensions must be observed to guarantee problem-free access to the device for service purposes:

- $A = 100 \text{ mm}$  (3.94 in)
- $L = L + 150 \text{ mm}$  (5.91 in)

### Inlet and outlet runs

To attain the specified level of accuracy of the measuring instrument, the inlet and outlet runs mentioned below must be maintained at the very minimum.



A0019189

12 Minimum inlet and outlet runs with various flow obstructions

*h* Difference in expansion

1 Reduction by one nominal diameter size

2 Single elbow (90° elbow)

3 Double elbow (2 × 90° elbows, opposite)

4 Double elbow 3D (2 × 90° elbows, opposite, not on one plane)

5 T-piece

6 Extension

7 Control valve

8 Two measuring instruments in a row where  $DN \leq 25$  (1''): directly flange on flange

9 Two measuring instruments in a row where  $DN \geq 40$  (1½''): for spacing, see graphic




- If there are several flow disturbances present, the longest specified inlet run must be maintained.
- If the required inlet runs cannot be observed, it is possible to install a specially designed flow conditioner → 52.

### Flow conditioner

If the inlet runs cannot be observed, the use of a flow conditioner is recommended.

The flow conditioner is fitted between two pipe flanges and centered by the mounting bolts. Generally this reduces the inlet run needed to  $10 \times DN$  with full measurement accuracy.



A0019208

### 1 Flow conditioner

The pressure loss for flow conditioners is calculated as follows:

$$\Delta p \text{ [mbar]} = 0.0085 \cdot \rho \text{ [kg/m}^3\text{]} \cdot v^2 \text{ [m/s]}$$

#### Example for steam

$p = 10 \text{ bar abs.}$

$t = 240 \text{ }^\circ\text{C} \rightarrow \rho = 4.39 \text{ kg/m}^3$

$v = 40 \text{ m/s}$

$$\Delta p = 0.0085 \cdot 4.39 \cdot 40^2 = 59.7 \text{ mbar}$$

#### Example for H<sub>2</sub>O condensate (80 °C)

$\rho = 965 \text{ kg/m}^3$

$v = 2.5 \text{ m/s}$

$$\Delta p = 0.0085 \cdot 965 \cdot 2.5^2 = 51.3 \text{ mbar}$$

$\rho$  : density of the process medium

$v$ : average flow velocity


abs. = absolute



- A specially designed flow conditioner is available as an accessory → 105.
- Dimensions of the flow conditioner → 73.

### Outlet runs when installing external devices

If installing an external device, observe the specified distance.



A0019205

PT Pressure

TT Temperature device

### Length of connecting cable

To ensure correct measuring results when using the remote version:


- Observe the maximum permitted cable length:  $L_{\text{max}} = 30 \text{ m (90 ft)}$ .
- The value for the cable length must be calculated if the cable cross-section differs from the specification.



For detailed information about calculating the length of the connecting cable, refer to the Operating Instructions for the device.

## Mounting the transmitter housing


### Wall mounting



A0033484

13 mm (in)

### Pipe mounting



A0033486


14 mm (in)

## Installation for delta heat measurements

- Order code for "Sensor version", option CA "Mass; 316L; 316L (integrated temperature measurement), -200 to +400 °C (-328 to +750 °F)"
- Order code for "Sensor version", option CB "Mass; Alloy C22; 316L (integrated temperature measurement), -200 to +400 °C (-328 to +750 °F)"
- Order code for "Sensor version", option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement), -200 to +400 °C (-328 to +750 °F)"
- Order code for "Sensor version", option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement), -40 to +100 °C (-40 to +212 °F)"

The second temperature measurement is taken using a separate temperature sensor. The measuring instrument reads in this value via a communication interface.

- In the case of saturated steam delta heat measurements, the measuring instrument must be installed on the steam side.
- In the case of water delta heat measurements, the device can be installed on the cold or warm side.



15 Layout for delta heat measurement of saturated steam and water



- 1 Measuring instrument
- 2 Temperature sensor
- 3 Heat exchanger
- Q Heat flow

Protective cover

A protective cover is available as an accessory for the device. It is used to protect against direct sunlight, precipitation and ice.

When installing the protective cover, a minimum upward clearance must be maintained:  
222 mm (8.74 in)

The protective cover can be ordered via the product structure together with the device:  
Order code for "Accessories enclosed" option PB "Protective cover"

 Ordered separately as an accessory →  104

Environment

Ambient temperature range

Compact version

Measuring instrument	Non-hazardous area:	-40 to +80 °C (-40 to +176 °F) <sup>1)</sup> -40 to +80 °C (-40 to +176 °F)
	Ex i, Ex nA, Ex ec:	-40 to +70 °C (-40 to +158 °F) <sup>1)</sup>
	Ex d, XP:	-40 to +60 °C (-40 to +140 °F) <sup>1)</sup>
	Ex d, Ex ia:	-40 to +60 °C (-40 to +140 °F) <sup>1)</sup>
Local display		-40 to +70 °C (-40 to +158 °F) <sup>2) 1)</sup>

- 1) Additionally available as order code for "Test, certificate", option JN "Transmitter ambient temperature -50 °C (-58 °F)". This option is only available in combination with a "High-temperature sensor -200 to +400 °C(-328 to +750 °F)", see order code 060 for "Sensor version; DSC sensor; measuring tube" with options BA, BB, CA, CB.
- 2) At temperatures below -20 °C (-4 °F), depending on the physical characteristics involved, it may no longer be possible to read the liquid crystal display.

Remote version

Transmitter	Non-hazardous area:	-40 to +80 °C (-40 to +176 °F) <sup>1)</sup> -40 to +80 °C (-40 to +176 °F)
	Ex i, Ex nA, Ex ec:	-40 to +80 °C (-40 to +176 °F) <sup>1)</sup>
	Ex d:	-40 to +60 °C (-40 to +140 °F) <sup>1)</sup>
	Ex d, Ex ia:	-40 to +60 °C (-40 to +140 °F) <sup>1)</sup>
Sensor	Non-hazardous area:	-40 to +85 °C (-40 to +185 °F) <sup>1)</sup>

	Ex i, Ex nA, Ex ec:	-40 to +85 °C (-40 to +185 °F) <sup>1)</sup>
	Ex d:	-40 to +85 °C (-40 to +185 °F) <sup>1)</sup>
	Ex d, Ex ia:	-40 to +85 °C (-40 to +185 °F) <sup>1)</sup>
<b>Local display</b>		-40 to +70 °C (-40 to +158 °F) <sup>2) 1)</sup>

- 1) Additionally available as order code for "Test, certificate", option JN "Transmitter ambient temperature -50 °C (-58 °F)". This option is only available in combination with a "High-temperature sensor -200 to +400 °C (-328 to +750 °F)", see order code 060 for "Sensor version; DSC sensor; measuring tube" with options BA, BB, CA, CB.
- 2) At temperatures < -20 °C (-4 °F), depending on the physical characteristics involved, it may no longer be possible to read the liquid crystal display.

- If operating outdoors:  
Avoid direct sunlight, particularly in warm climatic regions.

 You can order a weather protection cover from Endress+Hauser. →  104.

<b>Storage temperature</b>	<p>All components apart from the display modules: -50 to +80 °C (-58 to +176 °F)</p> <p><b>Display modules</b> -40 to +80 °C (-40 to +176 °F) Remote display FHX50: -40 to +80 °C (-40 to +176 °F)</p>
<b>Climate class</b>	DIN EN 60068-2-38 (test Z/AD)
<b>Degree of protection</b>	<p><b>Transmitter</b></p> <ul style="list-style-type: none"> <li>■ Standard: IP66/67, Type 4X enclosure, suitable for pollution degree 4</li> <li>■ When the housing is open: IP20, Type 1 enclosure, suitable for pollution degree 2</li> <li>■ Display module: IP20, Type 1 enclosure, suitable for pollution degree 2</li> </ul> <p><b>Sensor</b> IP66/67, Type 4X enclosure, suitable for pollution degree 4</p> <p><b>Device plug</b> IP67, only in screwed situation</p>
<b>Vibration-resistance and shock resistance</b>	<p><b>Vibration sinusoidal, in accordance with IEC 60068-2-6</b></p> <p>Order code for "Housing", option B "GT18 dual compartment, 316L, compact" and order code for "Sensor version; DSC sensor; Meas. tube", option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement)" or option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temp. measurement)"</p> <ul style="list-style-type: none"> <li>■ 2 to 8.4 Hz, 3.5 mm peak</li> <li>■ 8.4 to 500 Hz, 1 g peak</li> </ul> <p>Order code for "Housing", option C "GT20 dual compartment, alu, coated, compact" or option J "GT20 dual compartment, alu, coated, remote" or option K "GT18 dual compartment, 316L, remote"</p> <ul style="list-style-type: none"> <li>■ 2 to 8.4 Hz, 7.5 mm peak</li> <li>■ 8.4 to 500 Hz, 2 g peak</li> </ul> <p><b>Vibration broad-band random, according to IEC 60068-2-64</b></p> <p>Order code for "Housing", option B "GT18 dual compartment, 316L, compact" and order code for "Sensor version; DSC sensor; Meas. tube", option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement)" or option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temp. measurement)"</p> <ul style="list-style-type: none"> <li>■ 10 to 200 Hz, 0.003 g<sup>2</sup>/Hz</li> <li>■ 200 to 500 Hz, 0.001 g<sup>2</sup>/Hz</li> <li>■ Total: 0.93 g rms</li> </ul>



Order code for "Housing", option C "GT20 dual compartment, alu, coated, compact" or option J "GT20 dual compartment, alu, coated, remote" or option K "GT18 dual compartment, 316L, remote")

- 10 to 200 Hz, 0.01 g<sup>2</sup>/Hz
- 200 to 500 Hz, 0.003 g<sup>2</sup>/Hz
- Total: 1.67 g rms

**Half-sine shocks according to IEC 60068-2-27**

- Order code for "Housing", option B "GT18 dual compartment, 316L, compact" and order code for "Sensor version; DSC sensor; Meas. tube", option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement)" or option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temp. measurement)"  
6 ms 30 g
- Order code for "Housing", option C "GT20 dual compartment, alu, coated, compact" or option J "GT20 dual compartment, alu, coated, remote" or option K "GT18 dual compartment, 316L, remote")  
6 ms 50 g

**Rough handling shocks according to IEC 60068-2-31**

**Electromagnetic compatibility (EMC)**

- As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21), NAMUR Recommendation 21 (NE 21) is fulfilled when installed in accordance with NAMUR Recommendation 98 (NE 98)
- As per IEC/EN 61000-6-2 and IEC/EN 61000-6-4



Details are provided in the Declaration of Conformity.



This unit is not intended for use in residential environments and cannot guarantee adequate protection of the radio reception in such environments.


**Process**

**Medium temperature range**

*DSC sensor <sup>1)</sup>*

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Medium temperature range
AA	Volume; 316L; 316L	-40 to +260 °C (-40 to +500 °F), stainless steel
AB	Volume; Alloy C22; 316L	
BA	Volume high-temperature; 316L; 316L	-200 to +400 °C (-328 to +752 °F), stainless steel
BB	Volume high-temperature; Alloy C22; 316L	
CA	Mass; 316L; 316L	-200 to +400 °C (-328 to +752 °F), stainless steel
CB	Mass; Alloy C22; 316L	

1) Capacitance sensor

Order code for "Sensor version; DSC sensor; measuring tube"		
Option	Description	Medium temperature range
	For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies: <ul style="list-style-type: none"> <li>Only available for measuring instruments with the following communication protocols:               <ul style="list-style-type: none"> <li>HART</li> <li>PROFINET over Ethernet-APL</li> </ul> </li> <li>Oil-free or grease-free cleaning is not possible.</li> </ul>	
DA	Mass steam; 316L; 316L	-200 to +400 °C (-328 to +752 °F), stainless steel <sup>1) 2)</sup>
DB	Mass gas/liquid; 316L; 316L	-40 to +100 °C (-40 to +212 °F), stainless steel <sup>2)</sup>

- 1) Siphon enables use for extended temperature range (up to +400 °C (+752 °F)).
- 2) In steam applications, in conjunction with the siphon, the steam temperature may be higher (up to +400 °C (+752 °F)) than the permitted temperature of the pressure measuring cell. Without a siphon, the gas temperature is limited by the maximum permitted temperature of the pressure measuring cell. This applies regardless of whether or not a stop cock is present.

#### Pressure measuring cell

Order code for "Pressure component"		
Option	Description	Medium temperature range
B	Pressure measuring cell 2bar/29psi abs	-40 to +100 °C (-40 to +212 °F)
C	Pressure measuring cell 4bar/58psi abs	
D	Pressure measuring cell 10bar/145psi abs	
E	Pressure measuring cell 40bar/580psi abs	

#### Seals


Order code for "DSC sensor seal"		
Option	Description	Medium temperature range
A	Graphite	-200 to +400 °C (-328 to +752 °F)
B	Viton	-15 to +175 °C (+5 to +347 °F)
C	Gylon	-200 to +260 °C (-328 to +500 °F)
D	Kalrez	-20 to +275 °C (-4 to +527 °F)

#### Pressure/temperature ratings


The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.

The pressure-temperature rating for the specific measuring device is programmed into the software. If values exceed the curve range a warning is displayed. Depending on the system configuration and sensor version, the pressure and temperature are determined by entering, reading in or calculating values.




Integral mass vortex: The permitted pressure for the measuring device can be less than indicated in this section, depending on the selected pressure measuring cell. →  60

Flange connection: flange similar to EN 1092-1 (DIN 2501)




16 Flange connection material: stainless steel, multiple certifications, 1.4404/F316/F316L

Flange connection: flange similar to ASME B16.5



17 Flange connection material: stainless steel, multiple certifications, 1.4404/F316/F316L

Flange connection: flange similar to JIS B2220




18 Flange connection material: stainless steel, multiple certifications, 1.4404/F316/F316L


**Nominal pressure of sensor** The following overpressure resistance values apply to the sensor shaft in the event of a membrane rupture:


Sensor version; DSC sensor; measuring tube	Overpressure, sensor shaft in [bar a]
Volume	200
Volume high-temperature	200
Mass (integrated temperature measurement)	200
Mass steam (integrated pressure/temperature measurement) Mass gas/liquid (integrated pressure/temperature measurement)	200

## Pressure specifications

 For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:


- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.

The OPL (over pressure limit = sensor overload limit) for the measuring instrument depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to the measuring cell. Also observe pressure-temperature dependency. For the appropriate standards and further information →  45. The OPL may only be applied for a limited period of time.

The MWP (maximum working pressure) for the sensors depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to the measuring cell. Also observe pressure-temperature dependency. For the appropriate standards and further information →  45. The MWP may be applied at the device for an unlimited period. The MWP can also be found on the nameplate.

## WARNING

**The maximum pressure for the measuring instrument depends on the lowest-rated element with regard to pressure.**

- ▶ Note specifications regarding pressure range →  45.
- ▶ The Pressure Equipment Directive (2014/68/EU) uses the abbreviation "PS". The abbreviation "PS" corresponds to the MWP of the device.
- ▶ MWP: The MWP is indicated on the nameplate. This value refers to a reference temperature of +20 °C (+68°F) and may be applied to the device for an unlimited time. Note temperature dependence of MWP.
- ▶ OPL: The test pressure corresponds to the over pressure limit of the sensor and may be applied only temporarily to ensure that the measurement is within the specifications and no permanent damage occurs. In the case of sensor range and process connection combinations where the OPL of the process connection is less than the nominal value of the sensor, the device is set at the factory, at the very maximum, to the OPL value of the process connection. If using the entire sensor range, select a process connection with a higher OPL value.

Sensor	Maximum sensor measuring range		MWP	OPL
	Lower (LRL)	Upper (URL)		
	[bar (psi)]	[bar (psi)]		
2 bar (30 psi)	0 (0)	+2 (+30)	6.7 (100.5)	10 (150)
4 bar (60 psi)	0 (0)	+4 (+60)	10.7 (160.5)	16 (240)
10 bar (150 psi)	0 (0)	+10 (+150)	25 (375)	40 (600)
40 bar (600 psi)	0 (0)	+40 (+600)	100 (1 500)	160 (2 400)

## Pressure loss

For a precise calculation, use the Applicator →  106.


## Thermal insulation

For optimum temperature measurement and mass calculation, heat transfer at the sensor must be avoided for some fluids. This can be ensured by installing thermal insulation. A wide range of materials can be used for the required insulation.

This applies for:

- Compact version
- Remote sensor version

The maximum insulation height permitted is illustrated in the diagram:



A0019212


1 Maximum insulation height

- When insulating, ensure that a sufficiently large area of the housing support remains exposed.

The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.



The function of the siphon is to protect the measuring cell from excessively high steam process temperatures through the formation of condensate in the U-tube/circular pipe. To ensure the steam condenses, the siphon may only be insulated as far as the connection flange on the measuring tube side.



A0047532

19 Siphon

## Mechanical construction


### Dimensions in SI units



Pay attention to the information on diameter mismatch correction → 46.

### Compact version

Order code for "Housing", option B "GT18 dual compartment, 316L, compact"; option C "GT20 dual compartment, aluminum, coated, compact"



A0033794

20 Grayed out: Dualsens version

Single inner diameter line size reduction

Order code for "Process connection", option AAS/ABS/AFS/AGS/DDS/DES/D1S/D2S/D5S/D6S/NDS/NES/NFS/NGS											
DN	Reduction to DN	A <sup>1)</sup>	B	C <sup>1)</sup>	E <sup>2) 3) 4)</sup>	G	H	I <sup>5)</sup>	K (D <sub>i</sub> )	L	N <sup>6) 7)</sup>
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
25R	15	140.2	51.7	88.5	252	159.9	58.2	101.7	13.9	<sup>8)</sup>	<sup>9)</sup>
40R	25	140.2	51.7	88.5	258	159.9	58.2	101.7	24.3	<sup>8)</sup>	<sup>9)</sup>
50R	40	140.2	51.7	88.5	266	159.9	58.2	101.7	38.1	<sup>8)</sup>	532
80R	50	140.2	51.7	88.5	272	159.9	58.2	101.7	49.2	<sup>8)</sup>	544
100R	80	140.2	51.7	88.5	286	159.9	58.2	101.7	73.7	<sup>8)</sup>	571
150R	100	140.2	51.7	88.5	300	159.9	58.2	101.7	97	<sup>8)</sup>	600
200R	150	140.2	51.7	88.5	325	159.9	58.2	101.7	146.3	<sup>8)</sup>	650

- 1) For version with overvoltage protection: values + 8 mm
- 2) For version without local display: values - 10 mm
- 3) For high-temperature/low-temperature version: values + 29 mm
- 4) For p-T-compensated version
- 5) For version without local display: values - 7 mm
- 6) For version without local display: values - 20 mm
- 7) For high-temperature/low-temperature version: values + 58 mm
- 8) Dependent on respective flange connection
- 9) Not available as a Dualsens version


## Double inner diameter line size reduction

Order code for "Process connection", option AAS/ABS/AFS/AGS/DDS/DES/D1S/D2S/D5S/D6S/NDS/NES/NFS/NGS											
DN	Reduction to DN	A <sup>1)</sup>	B	C <sup>1)</sup>	E <sup>2) 3) 4)</sup>	G	H	I <sup>5)</sup>	K (D <sub>i</sub> )	L	N <sup>6) 7)</sup>
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
40S	15	140.2	51.7	88.5	252	159.9	58.2	101.7	13.9	<sup>8)</sup>	<sup>9)</sup>
50S	25	140.2	51.7	88.5	258	159.9	58.2	101.7	24.3		
80S	40	140.2	51.7	88.5	266	159.9	58.2	101.7	38.1		532
100S	50	140.2	51.7	88.5	272	159.9	58.2	101.7	49.2		544
150S	80	140.2	51.7	88.5	286	159.9	58.2	101.7	73.7		571
200S	100	140.2	51.7	88.5	300	159.9	58.2	101.7	97		600
250S	150	140.2	51.7	88.5	325	159.9	58.2	101.7	146.3		650

- 1) For version with overvoltage protection: values + 8 mm
- 2) For version without local display: values - 10 mm
- 3) For high-temperature/low-temperature version: values + 29 mm
- 4) For p-T-compensated version
- 5) For version without local display: values - 7 mm
- 6) For version without local display: values - 20 mm
- 7) For high-temperature/low-temperature version: values + 58 mm
- 8) Dependent on respective flange connection
- 9) Not available as a Dualsens version

## Transmitter remote version

Order code for "Housing", option J "GT20 dual compartment, aluminum, coated, remote"; option K "GT18 dual compartment, 316L, remote"




A0033796

A <sup>1)</sup>	B	C <sup>1)</sup>	F <sup>2)</sup>	G <sup>3)</sup>	Q	T <sup>3)</sup>
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
140.2	51.7	88.5	254	159.9	107	191

- 1) For version with overvoltage protection: value + 8 mm
- 2) For version without local display: value - 10 mm
- 3) For version without local display: value - 7 mm

## Sensor remote version

Order code for "Housing", option J "GT20 dual compartment, aluminum, coated, remote"; option K "GT18 dual compartment, 316L, remote"



A0033797

21 Grayed out: Dualsens version

#### Single inner diameter line size reduction

Order code for "Process connection", option AAS/ABS/AFS/AGS/DDS/DES/D1S/D2S/D5S/D6S/NDS/NES/NFS/NGS									
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	C [mm]	E <sup>1)</sup> [mm]	G [mm]	K (D <sub>i</sub> ) [mm]	L [mm]	N <sup>2)</sup> [mm]
25R	15	107.3	60.0	47.3	225	94.5	13.9	<sup>3)</sup>	<sup>4)</sup>
40R	25	107.3	60.0	47.3	231	94.5	24.3	<sup>3)</sup>	<sup>4)</sup>
50R	40	107.3	60.0	47.3	239	94.5	38.1	<sup>3)</sup>	477
80R	50	107.3	60.0	47.3	245	94.5	49.2	<sup>3)</sup>	489
100R	80	107.3	60.0	47.3	259	94.5	73.7	<sup>3)</sup>	517
150R	100	107.3	60.0	47.3	273	94.5	97	<sup>3)</sup>	545
200R	150	107.3	60.0	47.3	298	94.5	146.3	<sup>3)</sup>	596

- 1) For high-temperature/low-temperature version: values + 29 mm  
 2) For high-temperature/low-temperature version: values + 58 mm  
 3) Dependent on respective flange connection  
 4) Not available as a Dualsens version

#### Double inner diameter line size reduction

Order code for "Process connection", option AAS/ABS/AFS/AGS/DDS/DES/D1S/D2S/D5S/D6S/NDS/NES/NFS/NGS									
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	C [mm]	E <sup>1)</sup> [mm]	G [mm]	K (D <sub>i</sub> ) [mm]	L [mm]	N <sup>2)</sup> [mm]
40S	15	107.3	60.0	47.3	225	94.5	13.9	<sup>3)</sup>	<sup>4)</sup>
50S	25	107.3	60.0	47.3	231	94.5	24.3	<sup>3)</sup>	<sup>4)</sup>
80S	40	107.3	60.0	47.3	239	94.5	38.1	<sup>3)</sup>	477
100S	50	107.3	60.0	47.3	245	94.5	49.2	<sup>3)</sup>	489
150S	80	107.3	60.0	47.3	259	94.5	73.7	<sup>3)</sup>	517




Order code for "Process connection", option  
AAS/ABS/AFS/AGS/DDS/DES/D1S/D2S/D5S/D6S/NDS/NES/NFS/NGS

DN	Reducti on to DN	A	B	C	E <sup>1)</sup>	G	K (D <sub>i</sub> )	L	N <sup>2)</sup>
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
200S	100	107.3	60.0	47.3	273	94.5	97	<sup>3)</sup>	545
250S	150	107.3	60.0	47.3	298	94.5	146.3	<sup>3)</sup>	596

- 1) For high-temperature/low-temperature version: values + 29 mm  
 2) For high-temperature/low-temperature version: values + 58 mm  
 3) Dependent on respective flange connection  
 4) Not available as a Dualsens version

### Flange connections

#### Flange



A0015621



Length tolerance for dimension L in mm:

DN ≤ 100: +1.5 to -2.0 mm

DN ≥ 150: ±3.5 mm

#### Flange connection dimensions similar to DIN EN 1092-1: PN 10

Triple-certified material, 1.4404/F316/F316L

Order code for "Process connection", option DDS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
200R	150	340	295	8 × 22	24	146.3	300

Raised face in accordance with DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm

- 1) In compliance with ISO 13359 for DN 150.

#### Flange connection dimensions similar to DIN EN 1092-1: PN 10

Triple-certified material, 1.4404/F316/F316L

Order code for "Process connection", option DDS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
200S	100	340	295	8 × 22	26	112.0	300
250S	150	395	350	12 × 22	24	202.7	380

Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm

- 1) In compliance with ISO 13359 for DN 100 to 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 16</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option D1S</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
100R	80	220	180	8 × 18	22	87.0	250
150R	100	285	240	8 × 22	25	112.0	300
200R	150	340	295	12 × 22	24	146.3	300
Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm							

1) In compliance with ISO 13359 for DN 100 to 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 16</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option D1S</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
100S	50	220	180	8 × 18	24	62.0	250
150S	80	285	240	8 × 22	25	92.0	300
200S	100	340	295	12 × 22	27	112.0	300
250S	150	405	355	12 × 26	27	202.7	380
Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm							

1) In compliance with ISO 13359 for DN 100 to 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 16 with groove</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option D5S</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
100R	80	220	180	8 × 18	22	87.0	250
150R	100	285	240	8 × 22	25	112.0	300
Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm							

1) In compliance with ISO 13359 for DN 100 to 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 16 with groove</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option D5S</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
100S	50	220	180	8 × 18	24	62.0	250
150S	80	285	240	8 × 22	25	92.0	300
Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm							

1) In compliance with ISO 13359 for DN 100 to 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 25</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option DES</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
200R	150	360	310	12 × 26	30	146.3	300
Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm							

1) In compliance with ISO 13359 for DN 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 25</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option DES</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
200S	100	360	310	12 × 26	33.5	112.0	300
250S	150	425	370	12 × 30	32.0	202.7	380
Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm							

1) In compliance with ISO 13359 for DN 100 to 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 40</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option D2S</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
25R	15	115	85	4 × 14	18.0	22.0	200
40R	25	150	110	4 × 18	21.0	30.0	200
50R	40	165	125	4 × 18	22.0	45.0	200
80R	50	200	160	8 × 18	25.0	56.5	200
100R	80	235	190	8 × 22	26.5	87.0	250
150R	100	300	250	8 × 26	31.0	112.0	300
200R	150	375	320	12 × 30	36.5	146.3	300
Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm							

1) In compliance with ISO 13359 for DN 15 to 150.

<b>Flange connection dimensions similar to DIN EN 1092-1: PN 40</b> <b>Triple-certified material, 1.4404/F316/F316L</b> <b>Order code for "Process connection", option D2S</b>							
DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
40S	15	150	110	4 × 18	21.0	22.0	200
50S	25	165	125	4 × 18	21.0	30.0	200
80S	40	200	160	8 × 18	25.5	45.0	200
100S	50	235	190	8 × 22	27.5	62.0	250
150S	80	300	250	8 × 26	32.0	92.0	300
200S	100	375	320	12 × 30	38.5	112.0	300

**Flange connection dimensions similar to DIN EN 1092-1: PN 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option D2S**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
250S	150	450	385	12 × 33	39.0	202.7	380

Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm

1) In compliance with ISO 13359 for DN 15 to 150.

**Flange connection dimensions similar to DIN EN 1092-1: PN 40 with groove**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option D6S**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
25R	15	115	85	4 × 14	18.0	22.0	200
40R	25	150	110	4 × 18	21.0	30.0	200
50R	40	165	125	4 × 18	22.0	45.0	200
80R	50	200	160	8 × 18	25.0	56.5	200
100R	80	235	190	8 × 22	26.5	87.0	250
150R	100	300	250	8 × 26	31.0	112.0	300

Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm

1) In compliance with ISO 13359 for DN 15 to 100.

**Flange connection dimensions similar to DIN EN 1092-1: PN 40 with groove**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option D6S**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L <sup>1)</sup> [mm]
40S	15	150	110	4 × 18	21.0	22.0	200
50S	25	165	125	4 × 18	21.0	30.0	200
80S	40	200	160	8 × 18	25.5	45.0	200
100S	50	235	190	8 × 22	27.5	62.0	250
150S	80	300	250	8 × 26	32.0	92.0	300

Raised face according to DIN EN 1092-1 Form B1: Ra 6.3 to 12.5 µm

1) In compliance with ISO 13359 for DN 15 to 80.

**Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option AAS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
25R	15	108.0	79.2	4 × 15.7	18.0	22.0	200
40R	25	127.0	98.6	4 × 15.7	18.0	30.0	200
50R	40	152.4	120.7	4 × 19.1	20.0	45.0	200
80R	50	190.5	152.4	4 × 19.1	23.9	56.5	200
100R	80	228.6	190.5	8 × 19.1	24.5	87.0	250
150R	100	279.4	241.3	8 × 22.4	25.5	112.0	300

Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 40  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option AAS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
200R	150	342.9	298.5	8 × 22.4	28.4	146.3	300

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 40  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option AAS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
40S	15	127.0	98.6	4 × 15.7	19.0	22.0	200
50S	25	152.4	120.7	4 × 19.1	21.0	30.0	200
80S	40	190.5	152.4	4 × 19.1	25.0	45.0	200
100S	50	228.6	190.4	8 × 19.1	26.5	62.0	250
150S	80	279.4	241.3	8 × 22.4	26.0	92.0	300
200S	100	342.9	298.5	8 × 22.4	28.4	112.0	300
250S	150	406.4	362.0	12 × 25.4	31.4	202.7	380

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option AFS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
25R	15	108.0	79.2	4 × 15.7	18.5	22.0	200
40R	25	127.0	98.6	4 × 15.7	18.0	30.0	200
50R	40	152.4	120.7	4 × 19.1	20.0	45.0	200
80R	50	190.5	152.4	4 × 19.1	23.9	56.5	200
100R	80	228.6	190.5	8 × 19.1	24.5	87.0	250
150R	100	279.4	241.3	8 × 22.4	26.0	112.0	300

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option AFS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
40S	15	127.0	98.6	4 × 15.7	19.5	22	200
50S	25	152.4	120.7	4 × 19.1	21.0	30	200
80S	40	190.5	152.4	4 × 19.1	25.0	45	200
100S	50	228.6	190.4	8 × 19.1	26.5	62	250
150S	80	279.4	241.3	8 × 22.4	27.0	92	300

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

**Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option ABS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
25R	15	124.0	88.9	4 × 19.1	22.0	22.0	200
40R	25	155.4	114.3	4 × 22.4	25.0	30.0	200
50R	40	165.1	127.0	8 × 19.1	25.0	45.0	200
80R	50	209.6	168.1	8 × 22.4	28.9	56.5	200
100R	80	254.0	200.2	8 × 22.4	31.8	87.0	250
150R	100	317.5	269.7	12 × 22.4	38.5	112.0	300
200R	150	381.0	330.2	12 × 25.4	41.1	146.3	300

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

**Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option ABS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
40S	15	155.4	114.3	4 × 22.4	27.0	22.0	200
50S	25	165.1	127.0	8 × 19.1	26.0	30.0	200
80S	40	209.6	168.1	8 × 22.4	37.9	45.0	200
100S	50	254.0	200.2	8 × 22.4	31.8	62.0	250
150S	80	317.5	269.7	12 × 22.4	41.5	92.0	300
200S	100	381.0	330.2	12 × 25.4	47.5	112.0	300
250S	150	444.5	387.4	16 × 28.4	46.9	202.7	380

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

**Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 80**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option AGS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
25R	15	124.0	88.9	4 × 19.1	22.0	22.0	200
40R	25	155.4	114.3	4 × 22.4	25.0	30.0	200
50R	40	165.1	127.0	8 × 19.1	25.0	45.0	200
80R	50	209.6	168.1	8 × 22.4	28.9	56.5	200
100R	80	254.0	200.2	8 × 22.4	31.8	87.0	250
150R	100	317.5	269.7	12 × 22.4	39.0	112.0	300

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

**Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 80**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option AGS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
40S	15	155.4	114.3	4 × 22.4	27.0	22	200
50S	25	165.1	127.0	8 × 19.1	26.0	30	200
80S	40	209.6	168.1	8 × 22.4	37.9	45	200
100S	50	254.0	200.2	8 × 22.4	31.8	62	250
150S	80	317.5	269.7	12 × 22.4	42.0	92	300

Raised face in accordance with ASME 16.5: Ra 3.2 to 6.3 µm

**Flange connection dimensions similar to JIS B2220: 10K, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option NDS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
50R	40	155	120	4 × 19	20.0	45.0	200
80R	50	185	150	8 × 19	22.0	56.5	200
100R	80	210	175	8 × 19	22.0	87.0	250
150R	100	280	240	8 × 23	31.0	112.0	300
200R	150	330	290	12 × 23	26.5	146.3	300

Raised face in accordance with: Ra 3.2 to 6.3 µm

**Flange connection dimensions similar to JIS B2220: 10K, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option NDS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
50S	25	155	120	4 × 19	20.5	30.0	200
80S	40	185	150	8 × 19	22.0	45.0	200
100S	50	210	175	8 × 19	25.5	62.0	250
150S	80	280	240	8 × 23	31.0	92.0	300
200S	100	330	290	12 × 23	33.5	112.0	300
250S	150	400	355	12 × 25	30.5	202.7	380

Raised face in accordance with JIS 2220: Ra 3.2 to 6.3 µm

**Flange connection dimensions similar to JIS B2220: 10K, Schedule 80**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option NFS**

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
50R	40	155	120	4 × 19	20.0	45.0	200
80R	50	185	150	8 × 19	22.0	56.5	200
100R	80	210	175	8 × 19	22.0	87.0	250
150R	100	280	240	8 × 23	31.5	112.0	300

Raised face in accordance with JIS 2220: Ra 3.2 to 6.3 µm

Flange connection dimensions similar to JIS B2220: 10K, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option NFS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
50S	25	155	120	4 × 19	20.5	30	200
80S	40	185	150	8 × 19	22.0	45	200
100S	50	210	175	8 × 19	26.0	62	250
150S	80	280	240	8 × 23	31.5	92	300

Raised face in accordance with JIS 2220: Ra 3.2 to 6.3 µm

Flange connection dimensions similar to JIS B2220: 20K, Schedule 40  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option NES

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
25R	15	125	90	4 × 19	18.5	22.0	200
40R	25	140	105	4 × 19	18.5	30.0	200
50R	40	155	120	8 × 19	20.0	45.0	200
80R	50	200	160	8 × 23	26.5	56.5	200
100R	80	225	185	8 × 23	25.5	87.0	250
150R	100	305	260	12 × 25	37.5	112.0	300
200R	150	350	305	12 × 25	31.0	146.3	300

Raised face in accordance with JIS 2220: Ra 3.2 to 6.3 µm

Flange connection dimensions similar to JIS B2220: 20K, Schedule 40  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option NES

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
40S	15	140	105	4 × 19	20.5	22.0	200
50S	25	155	120	8 × 19	21.0	30.0	200
80S	40	200	160	8 × 23	25.5	45.0	200
100S	50	225	185	8 × 23	29.0	62.0	250
150S	80	305	260	12 × 25	38.5	92.0	300
200S	100	350	305	12 × 25	43.5	112.0	300
250S	150	430	380	12 × 27	37.0	202.7	380

Raised face in accordance with JIS 2220: Ra 3.2 to 6.3 µm

Flange connection dimensions similar to JIS B2220: 20K, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option NGS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
25R	15	125	90	4 × 19	18.5	22.0	200
40R	25	140	105	4 × 19	19.0	30.0	200
50R	40	155	120	8 × 19	22.0	45.0	200



Flange connection dimensions similar to JIS B2220: 20K, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option NGS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
80R	50	200	160	8 × 23	27.0	56.5	200
100R	80	225	185	8 × 23	26.0	87.0	250
150R	100	305	260	12 × 25	37.5	112.0	300

Raised face in accordance with JIS 2220: Ra 3.2 to 6.3 µm


Flange connection dimensions similar to JIS B2220: 20K, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option NGS

DN [mm]	Reduction to DN [mm]	A [mm]	B [mm]	Ø C [mm]	D [mm]	E [mm]	L [mm]
40S	15	140	105	4 × 19	20.5	22	200
50S	25	155	120	8 × 19	21.0	30	200
80S	40	200	160	8 × 23	25.5	45	200
100S	50	225	185	8 × 23	29.5	62	250
150S	80	305	260	12 × 25	39.0	92	300

Raised face in accordance with JIS 2220: Ra 3.2 to 6.3 µm

## Accessories

### Flow conditioner



A0033504

Used in combination with flanges similar to DIN EN 1092-1: PN 10  
 1.4404 (316, 316L)  
 Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5
40	95.3	D1	5.3
50	110.0	D2	6.8
80	145.3	D2	10.1
100	165.3	D2	13.3
150	221.0	D2	20.0

Used in combination with flanges similar to DIN EN 1092-1: PN 10

1.4404 (316, 316L)

Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
200	274.0	D1	26.3
250	330.0	D2	33.0

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges similar to DIN EN 1092-1: PN 16

1.4404 (316, 316L)

Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5
40	95.3	D1	5.3
50	110.0	D2	6.8
80	145.3	D2	10.1
100	165.3	D2	13.3
150	221.0	D2	20.0
200	274.0	D2	26.3
250	330.0	D2	33.0

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges similar to DIN EN 1092-1: PN 25

1.4404 (316, 316L)

Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5
40	95.3	D1	5.3
50	110.0	D2	6.8
80	145.3	D2	10.1
100	171.3	D1	13.3
150	227.0	D2	20.0
200	280.0	D1	26.3
250	340.0	D1	33.0

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges similar to DIN EN 1092-1: PN 40 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5
40	95.3	D1	5.3
50	110.0	D2	6.8
80	145.3	D2	10.1
100	171.3	D1	13.3
150	227.0	D2	20.0
200	294.0	D2	26.3
250	355.0	D2	33.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.  
 2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges similar to ASME B16.5: Class 150 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	50.1	D1	2.0
25	69.2	D2	3.5
40	88.2	D2	5.3
50	106.6	D2	6.8
80	138.4	D1	10.1
100	176.5	D2	13.3
150	223.5	D1	20.0
200	274.0	D1	26.3
250	340.0	D1	33.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.  
 2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges similar to ASME B16.5: Class 300 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	56.5	D1	2.0
25	74.3	D1	3.5
40	97.7	D2	5.3
50	113.0	D1	6.8
80	151.3	D1	10.1
100	182.6	D1	13.3
150	252.0	D1	20.0

Used in combination with flanges similar to ASME B16.5: Class 300

1.4404 (316, 316L)

Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
200	309.0	D1	26.3
250	363.0	D1	33.0

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges similar to JIS B2220: 10K

1.4404 (316, 316L)

Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	60.3	D2	2.0
25	76.3	D2	3.5
40	91.3	D2	5.3
50	106.6	D2	6.8
80	136.3	D2	10.1
100	161.3	D2	13.3
150	221.0	D2	20.0
200	271.0	D2	26.3
250	330.0	D2	33.0

1) The flow conditioner is fitted at the outer diameter between the bolts.

2) The flow conditioner is fitted at the indentations between the bolts.

Used in combination with flanges similar to JIS B2220: 20K

1.4404 (316, 316L)

Order code for "Accessory enclosed", option PF


DN [mm]	Centering diameter [mm]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [mm]
15	60.3	D2	2.0
25	76.3	D2	3.5
40	91.3	D2	5.3
50	106.6	D2	6.8
80	142.3	D1	10.1
100	167.3	D1	13.3
150	240.0	D1	20.0
200	284.0	D1	26.3
250	355.0	D2	33.0

1) The flow conditioner is fitted at the outer diameter between the bolts.


2) The flow conditioner is fitted at the indentations between the bolts.

Pressure measuring cell

- i** For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:
- Only available for measuring instruments with the following communication protocols:
    - HART
    - PROFINET over Ethernet-APL
  - Oil-free or grease-free cleaning is not possible.



Order code for "Sensor version; DSC sensor; measuring tube": Option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement)"							
DN [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	G [mm]	L [mm]
40R, 50S	76	78.8	155	60.8	190.5	407	307
50R, 80S	76	78.8	155	60.8	190.5	407	314
80R, 100S	76	78.8	155	60.8	190.5	407	320
100R, 150S	76	78.8	155	60.8	190.5	407	331
150R, 200S	76	78.8	155	60.8	190.5	407	346
200R, 250S	76	78.8	155	60.8	190.5	407	372



A0034024

Order code for "Sensor version; DSC sensor; measuring tube":  
Option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement)"

DN [mm]	A [mm]	B [mm]	C [mm]	L [mm]
40R, 50S	191	134	78.8	324
50R, 80S	191	140	78.8	331
80R, 100S	191	146	78.8	337
100R, 150S	191	158	78.8	348
150R, 200S	191	172	78.8	363
200R, 250S	191	198	78.8	389


#### Dimensions in US units



Pay attention to the information on diameter mismatch correction → 46.

#### Compact version

Order code for "Housing", option B "GT18 dual compartment, 316L, compact"; option C "GT20 dual compartment, aluminum, coated, compact"



A0033794

22 Grayed out: Dualsens version

*Single inner diameter line size reduction*

Order code for "Process connection", option AAS/ABS/AFS/AGS											
DN [in]	Reduction to DN [in]	A <sup>1)</sup> [in]	B [in]	C <sup>1)</sup> [in]	E <sup>2) 3) 4)</sup> [in]	G [in]	H [in]	I <sup>5)</sup> [in]	K (D <sub>i</sub> ) [in]	L [in]	N <sup>6) 7)</sup> [in]
1R	½	5.52	2.04	3.48	9.92	6.3	2.29	4	0.55	<sup>8)</sup>	<sup>9)</sup>
1½R	1	5.52	2.04	3.48	10.2	6.3	2.29	4	0.96	<sup>8)</sup>	<sup>9)</sup>
2R	1½	5.52	2.04	3.48	10.5	6.3	2.29	4	1.5	<sup>8)</sup>	20.9
3R	2	5.52	2.04	3.48	10.7	6.3	2.29	4	1.94	<sup>8)</sup>	21.4
4R	3	5.52	2.04	3.48	11.3	6.3	2.29	4	2.9	<sup>8)</sup>	22.5
6R	4	5.52	2.04	3.48	11.8	6.3	2.29	4	3.82	<sup>8)</sup>	23.6
8R	6	5.52	2.04	3.48	12.8	6.3	2.29	4	5.76	<sup>8)</sup>	25.6

- 1) For version with overvoltage protection: values + 0.31 in
- 2) For version without local display: values - 0.39 in
- 3) For p-T-compensated version
- 4) For high-temperature/low-temperature version: values + 1.14 in
- 5) For version without local display: values - 0.28 in
- 6) For version without local display: values - 0.78 in
- 7) For high-temperature/low-temperature version: values + 2.28 in
- 8) Dependent on respective flange connection
- 9) Not available as a Dualsens version


*Double inner diameter line size reduction*

Order code for "Process connection", option AAS/ABS/AFS/AGS											
DN [in]	Reduction to DN [in]	A <sup>1)</sup> [in]	B [in]	C <sup>1)</sup> [in]	E <sup>2) 3) 4)</sup> [in]	G [in]	H [in]	I <sup>5)</sup> [in]	K (D <sub>i</sub> ) [in]	L [in]	N <sup>6) 7)</sup> [in]
1½S	½	5.52	2.04	3.48	9.92	6.3	2.29	4	0.55	<sup>8)</sup>	<sup>9)</sup>
2S	1	5.52	2.04	3.48	10.2	6.3	2.29	4	0.96		
3S	1½	5.52	2.04	3.48	10.5	6.3	2.29	4	1.5		20.9
4S	2	5.52	2.04	3.48	10.7	6.3	2.29	4	1.94		21.4
6S	3	5.52	2.04	3.48	11.3	6.3	2.29	4	2.9		22.5
8S	4	5.52	2.04	3.48	11.8	6.3	2.29	4	3.82		23.6
10S	6	5.52	2.04	3.48	12.8	6.3	2.29	4	5.76		25.6

- 1) For version with overvoltage protection: values + 0.31 in
- 2) For version without local display: values - 0.39 in
- 3) For high-temperature/low-temperature version: values + 1.14 in
- 4) For p-T-compensated version
- 5) For version without local display: values - 0.28 in
- 6) For version without local display: values - 0.78 in
- 7) For high-temperature/low-temperature version: values + 2.28 in
- 8) Dependent on respective flange connection
- 9) Not available as a Dualsens version

**Transmitter remote version**

Order code for "Housing", option J "GT20 dual compartment, aluminum, coated, remote"; option K "GT18 dual compartment, 316L, remote"




A0033796

A <sup>1)</sup> [in]	B [in]	C <sup>1)</sup> [in]	F <sup>2)</sup> [in]	G <sup>3)</sup> [in]	Q [in]	T <sup>3)</sup> [in]
5.52	2.04	3.48	10	6.3	4.21	7.52

- 1) For version with overvoltage protection: value + 0.31 in  
 2) For version without local display: value - 0.39 in  
 3) For version without local display: value - 0.28 in

#### Sensor remote version

Order code for "Housing", option J "GT20 two-chamber, aluminum, coated, remote"; option K "GT18 two-chamber, 316L, remote"



A0033797

23 Grayed out: Dualsens version

#### Single inner diameter line size reduction

Flange similar to ASME B16.5: Class 150/300, Schedule 40/80  
 Stainless steel ,1.4404  
 Order code for "Process connection", option AAS/ABS/AFS/AGS

DN [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	E <sup>1)</sup> [in]	G [in]	K (D <sub>i</sub> ) [in]	L [in]	N <sup>2)</sup> [in]
1R	½	4.22	2.36	1.86	8.86	3.72	0.55	<sup>3)</sup>	<sup>4)</sup>
1½R	1	4.22	2.36	1.86	9.09	3.72	0.96	<sup>3)</sup>	<sup>4)</sup>
2R	1½	4.22	2.36	1.86	9.41	3.72	1.5	<sup>3)</sup>	18.8



<b>Flange similar to ASME B16.5: Class 150/300, Schedule 40/80</b> <b>Stainless steel ,1.4404</b> <b>Order code for "Process connection", option AAS/ABS/AFS/AGS</b>									
DN	Reduction to DN	A	B	C	E <sup>1)</sup>	G	K (D <sub>i</sub> )	L	N <sup>2)</sup>
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3R	2	4.22	2.36	1.86	9.65	3.72	1.94	<sup>3)</sup>	19.3
4R	3	4.22	2.36	1.86	10.2	3.72	2.9	<sup>3)</sup>	20.4
6R	4	4.22	2.36	1.86	10.7	3.72	3.82	<sup>3)</sup>	21.5
8R	6	4.22	2.36	1.86	11.7	3.72	5.76	<sup>3)</sup>	23.5

- 1) For high-temperature/low-temperature version: values +1.14 in  
2) For high-temperature/low-temperature version: values + 2.28 in  
3) Dependent on respective flange connection  
4) Not available as a Dualsens version


*Double inner diameter line size reduction*

<b>Flange similar to ASME B16.5: Class 150/300, Schedule 40/80</b> <b>Stainless steel ,1.4404</b> <b>Order code for "Process connection", option AAS/ABS/AFS/AGS</b>									
DN	Reduction to DN	A	B	C	E <sup>1)</sup>	G	K (D <sub>i</sub> )	L	N <sup>2)</sup>
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
1½S	½	4.22	2.36	1.86	8.86	3.72	0.55	<sup>3)</sup>	<sup>4)</sup>
2S	1	4.22	2.36	1.86	9.09	3.72	0.96	<sup>3)</sup>	<sup>4)</sup>
3S	1½	4.22	2.36	1.86	9.41	3.72	1.5	<sup>3)</sup>	18.8
4S	2	4.22	2.36	1.86	9.65	3.72	1.94	<sup>3)</sup>	19.3
6S	3	4.22	2.36	1.86	10.2	3.72	2.9	<sup>3)</sup>	20.4
8S	4	4.22	2.36	1.86	10.7	3.72	3.82	<sup>3)</sup>	21.5
10S	6	4.22	2.36	1.86	11.7	3.72	5.76	<sup>3)</sup>	23.5

- 1) For high-temperature/low-temperature version: values +1.14 in  
2) For high-temperature/low-temperature version: values + 2.28 in  
3) Dependent on respective flange connection  
4) Not available as a Dualsens version

## Flange connections

### Flange



A0015621



Length tolerance for dimension L in inches:

DN ≤ 4": +0.06 to -0.08 in

DN ≥ 6": ±0.14 in

**Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option AAS**

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1R	½	4.26	3.12	4 × Ø0.62	0.71	0.87	7.87
1½R	1	5	3.88	4 × Ø0.62	0.71	1.18	7.87
2R	1½	6	4.75	4 × Ø0.75	0.79	1.77	7.87
3R	2	7.5	6	4 × Ø0.75	0.94	2.22	7.87
4R	3	9	7.5	8 × Ø0.75	0.96	3.43	9.84
6R	4	11	9.5	8 × Ø0.88	1	4.41	11.8
8R	6	13.5	11.8	8 × Ø0.88	1.12	5.76	11.8

Raised face according to ASME B16.5: Ra 125 to 250µin

**Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option AAS**

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1½S	½	5	3.88	4 × Ø0.62	0.75	0.87	7.87
2S	1	6	4.75	4 × Ø0.75	0.83	1.18	7.87
3S	1½	7.5	6	4 × Ø0.75	0.98	1.77	7.87
4S	2	9	7.5	8 × Ø0.75	1.04	2.44	9.84
6S	3	11	9.5	8 × Ø0.88	1.04	3.62	11.8
8S	4	13.5	11.8	8 × Ø0.88	1.12	4.41	11.8
10S	6	16	14.3	12 × Ø1	1.24	7.98	15

Raised face according to ASME B16.5: Ra 125 to 250µin

**Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 80**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option AFS**

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1R	½	4.26	3.12	4 × Ø0.62	0.73	0.87	7.87
1½R	1	5	3.88	4 × Ø0.62	0.71	1.18	7.87
2R	1½	6	4.75	4 × Ø0.75	0.79	1.77	7.87
3R	2	7.5	6	4 × Ø0.75	0.94	2.22	7.87
4R	3	9	7.5	8 × Ø0.75	0.96	3.43	9.84
6R	4	11	9.5	8 × Ø0.88	1.02	4.41	11.8

Raised face according to ASME B16.5: Ra 125 to 250µin

**Flange connection dimensions similar to ASME B16.5: Class 150, Schedule 80**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option AFS**

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1½S	½	5	3.88	4 × Ø0.62	0.77	0.87	7.87
2S	1	6	4.75	4 × Ø0.75	0.83	1.18	7.87
3S	1½	7.5	6	4 × Ø0.75	0.98	1.77	7.87
4S	2	9	7.5	8 × Ø0.75	1.04	2.44	9.84
6S	3	11	9.5	8 × Ø0.88	1.06	3.62	11.8

Raised face according to ASME B16.5: Ra 125 to 250µin

**Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option ABS**

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1R	½	4.89	3.5	4 × Ø0.75	0.87	0.87	7.87
1½R	1	6.12	4.5	4 × Ø0.88	0.99	1.18	7.87
2R	1½	6.5	5	8 × Ø0.75	0.99	1.77	7.87
3R	2	8.25	6.62	8 × Ø0.88	1.14	2.22	7.87
4R	3	10	7.88	8 × Ø0.88	1.25	3.43	9.84
6R	4	11.8	10.6	12 × Ø0.88	1.52	4.41	11.80
8R	6	15	13	12 × Ø1	1.62	5.76	11.80

Raised face according to ASME B16.5: Ra 125 to 250µin

**Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 40**  
**Triple-certified material, 1.4404/F316/F316L**  
**Order code for "Process connection", option ABS**

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1½S	½	6.12	4.5	4 × Ø0.88	1.06	0.87	7.87
2S	1	6.5	5	8 × Ø0.75	1.02	1.18	7.87
3S	1½	8.25	6.62	8 × Ø0.88	1.49	1.77	7.87

Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 40  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option ABS

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
4S	2	10	7.88	8 × Ø0.88	1.25	2.44	9.84
6S	3	12.5	10.6	12 × Ø0.88	1.63	3.62	11.8
8S	4	15	13	12 × Ø1	1.87	4.41	11.8
10S	6	17.5	15.3	16 × Ø1.12	1.85	7.98	15

Raised face according to ASME B16.5: Ra 125 to 250µin

Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option AGS

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1R	½	4.89	3.5	4 × Ø0.75	0.87	0.87	7.87
1½R	1	6.12	4.5	4 × Ø0.88	0.99	1.18	7.87
2R	1½	6.5	5	8 × Ø0.75	0.99	1.77	7.87
3R	2	8.25	6.62	8 × Ø0.88	1.14	2.22	7.87
4R	3	10	7.88	8 × Ø0.88	1.25	3.43	9.84
6R	4	11.8	10.6	12 × Ø0.88	1.54	4.41	11.8

Raised face according to ASME B16.5: Ra 125 to 250µin


Flange connection dimensions similar to ASME B16.5: Class 300, Schedule 80  
 Triple-certified material, 1.4404/F316/F316L  
 Order code for "Process connection", option AGS

NPS [in]	Reduction to DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1½S	½	6.12	4.5	4 × Ø0.88	1.06	0.87	7.87
2S	1	6.5	5	8 × Ø0.75	1.02	1.18	7.87
3S	1½	8.25	6.62	8 × Ø0.88	1.49	1.77	7.87
4S	2	10	7.88	8 × Ø0.88	1.25	2.44	9.84
6S	3	12.5	10.6	12 × Ø0.88	1.65	3.62	11.8

Raised face according to ASME B16.5: Ra 125 to 250µin

Accessories

Flow conditioner



Used in combination with flanges similar to ASME B16.5: Class 150 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [in]	Centering diameter [in]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [in]
½	1.97	D1	0.08
1	2.72	D2	0.14
1½	3.47	D2	0.21
2	4.09	D2	0.27
3	5.45	D1	0.40
4	6.95	D2	0.52
6	8.81	D1	0.79
8	10.80	D1	1.04
10	13.40	D1	1.30

- 1) The flow conditioner is fitted at the outer diameter between the bolts.  
2) The flow conditioner is fitted at the indentations between the bolts.


Used in combination with flanges similar to ASME B16.5: Class 300 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [in]	Centering diameter [in]	D1 <sup>1)</sup> /D2 <sup>2)</sup>	s [in]
½	2.22	D1	0.08
1	2.93	D1	0.14
1½	3.85	D2	0.21
2	4.45	D1	0.27
3	5.96	D1	0.40
4	7.19	D1	0.52
6	9.92	D1	0.79
8	12.20	D1	1.04
10	14.30	D1	1.30

- 1) The flow conditioner is fitted at the outer diameter between the bolts.  
2) The flow conditioner is fitted at the indentations between the bolts.

## Pressure measuring cell

**i** For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:


- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.



Order code for "Sensor version; DSC sensor; measuring tube":

Option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement)"

DN [in]	B [in]	C [in]	D [in]	E [in]	F [in]	G [in]	L [in]
1½R, 2S	2.99	3.1	6.1	2.39	7.5	16.02	12.09
2R, 3S	2.99	3.1	6.1	2.39	7.5	16.02	12.36
3R, 4S	2.99	3.1	6.1	2.39	7.5	16.02	12.6
4R, 6S	2.99	3.1	6.1	2.39	7.5	16.02	13.03
6R, 8S	2.99	3.1	6.1	2.39	7.5	16.02	13.62
8R, 10S	2.99	3.1	6.1	2.39	7.5	16.02	14.65



A0034024

Order code for "Sensor version; DSC sensor; measuring tube": Option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement)"				
DN [in]	A [in]	B [in]	C [in]	L [in]
1½R, 2S	7.52	5.28	3.1	12.76
2R, 3S	7.52	5.51	3.1	13.03
3R, 4S	7.52	5.75	3.1	13.27
4R, 6S	7.52	6.22	3.1	13.7
6R, 8S	7.52	6.77	3.1	14.29
8R, 10S	7.52	7.8	3.1	15.31

Weight

Compact version

Single inner diameter line size reduction

Weight data:

- Including the transmitter:
  - Order code for "Housing", option C "GT20, two-chamber, aluminum, coated, compact" 1.8 kg (4.0 lb):
  - Order code for "Housing", option B "GT18 two-chamber, 316L, compact" 4.5 kg (9.9 lb):
- Excluding packaging material

Weight in SI units

All values (weight) refer to devices with EN (DIN), PN 40 flanges. Weight information in [kg].

DN [mm]	Internal diameter [mm]	Weight [kg]	
		Order code for "Housing", option C "GT20 two-chamber, aluminum, coated, compact" <sup>1)</sup>	Order code for "Housing", option B "GT18 two-chamber, 316L, compact" <sup>1)</sup>
25R	15	6.1	8.8
40R	25	10.1	12.8
50R	40	12.1	14.8
80R	50	16.1	18.8
100R	80	23.1	25.8
150R	100	42.1	44.8
200R	150	63.1	65.8

1) For high-temperature/low-temperature version: values + 0.2 kg

*Weight in US units*

All values (weight) refer to devices with ASME B16.5, Class 300/Sch. 40 flanges. Weight information in [lbs].

DN [in]	Internal diameter [in]	Weight [lbs]	
		Order code for "Housing", option C "GT20 two-chamber, aluminum, coated, compact" <sup>1)</sup>	Order code for "Housing", option B "GT18 two-chamber, 316L, compact" <sup>1)</sup>
1R	½	18.0	23.9
1½R	1	22.4	28.3
2R	1½	26.8	32.7
3R	2	48.8	54.8
4R	3	68.7	74.6
6R	4	121.6	127.5
8R	6	165.7	171.6

1) For high-temperature/low-temperature version: values + 0.4 lbs

**Transmitter remote version***Wall-mount housing*

Dependent on the material of wall-mount housing:

- Order code for "Housing" option J "GT20 two-chamber, aluminum, coated, remote" 2.4 kg (5.2 lb):
- Order code for "Housing", option K "GT18 two-chamber, 316L, remote" 6.0 kg (13.2 lb):

**Sensor remote version***Single inner diameter line size reduction*

Weight data:

- Including sensor connection housing:
  - Order code for "Housing" option J "GT20 two-chamber, aluminum, coated, remote" 0.8 kg (1.8 lb):
  - Order code for "Housing", option K "GT18 two-chamber, 316L, remote" 2.0 kg (4.4 lb):
- Excluding the connecting cable
- Excluding packaging material

*Weight in SI units*

All values (weight) refer to devices with EN (DIN), PN 40 flanges. Weight information in [kg].

DN [mm]	Internal diameter [mm]	Weight [kg]	
		sensor connection housing Order code for "Housing", option J "GT20 two-chamber, aluminum, coated, remote" <sup>1)</sup>	sensor connection housing Order code for "Housing", option K "GT18 two-chamber, 316L, remote" <sup>1)</sup>
25R	15	5.1	6.3
40R	25	9.1	10.3
50R	40	11.1	12.3
80R	50	15.1	16.3
100R	80	22.1	23.3
150R	100	41.1	42.3
200R	150	62.1	63.3

1) For high-temperature/low-temperature version: values + 0.2 kg



*Weight in US units*

All values (weight) refer to devices with ASME B16.5, Class 300/Sch. 40 flanges. Weight information in [lbs].

DN [in]	Internal diameter [in]	Weight [lbs]	
		sensor connection housing Order code for "Housing", option J "GT20 two-chamber, aluminum, coated, remote" <sup>1)</sup>	sensor connection housing Order code for "Housing", option K "GT18 two-chamber, 316L, remote" <sup>1)</sup>
1R	½	15.6	18.3
1½R	1	20.0	22.7
2R	1½	24.4	27.2
3R	2	46.4	49.2
4R	3	66.3	69.0
6R	4	119.2	122.0
8R	6	163.3	166.0

1) For high-temperature/low-temperature version: values + 0.4 lbs

**Accessories***Flow conditioner**Weight in SI units*

DN <sup>1)</sup> [mm]	Pressure rating	Weight [kg]
15	PN 10 to 40	0.04
25	PN 10 to 40	0.1
40	PN 10 to 40	0.3
50	PN 10 to 40	0.5
80	PN 10 to 40	1.4
100	PN10 to 40	2.4
150	PN 10/16 PN 25/40	6.3 7.8
200	PN 10 PN 16/25 PN 40	11.5 12.3 15.9
250	PN 10 to 25 PN 40	25.7 27.5

1) EN (DIN)

DN <sup>1)</sup> [mm]	Pressure rating	Weight [kg]
15	Class 150 Class 300	0.03 0.04
25	Class 150 Class 300	0.1
40	Class 150 Class 300	0.3
50	Class 150 Class 300	0.5

DN <sup>1)</sup> [mm]	Pressure rating	Weight [kg]
80	Class 150 Class 300	1.2 1.4
100	Class 150 Class 300	2.7
150	Class 150 Class 300	6.3 7.8
200	Class 150 Class 300	12.3 15.8
250	Class 150 Class 300	25.7 27.5

1) ASME

DN <sup>1)</sup> [mm]	Pressure rating	Weight [kg]
15	20K	0.06
25	20K	0.1
40	20K	0.3
50	10K 20K	0.5
80	10K 20K	1.1
100	10K 20K	1.80
150	10K 20K	4.5 5.5
200	10K 20K	9.2
250	10K 20K	15.8 19.1

1) JIS

*Weight in US units*

DN <sup>1)</sup> [in]	Pressure rating	Weight [lbs]
½	Class 150 Class 300	0.07 0.09
1	Class 150 Class 300	0.3
1½	Class 150 Class 300	0.7
2	Class 150 Class 300	1.1
3	Class 150 Class 300	2.6 3.1
4	Class 150 Class 300	6.0
6	Class 150 Class 300	14.0 16.0

DN <sup>1)</sup> [in]	Pressure rating	Weight [lbs]
8	Class 150 Class 300	27.0 35.0
10	Class 150 Class 300	57.0 61.0

1) ASME

## Materials

### Transmitter housing


#### Compact version

- Order code for "Housing", option B "GT18 two-chamber, 316L, compact":  
Stainless steel, CF3M
- Order code for "Housing", option C "GT20, two-chamber, aluminum, coated, compact":  
Aluminum, AlSi10Mg, coated
- Window material: glass

#### Remote version

- Order code for "Housing" option J "GT20 two-chamber, aluminum, coated, remote":  
Aluminum, AlSi10Mg, coated
- Order code for "Housing", option K "GT18 two-chamber, 316L, remote":  
For maximum corrosion resistance: Stainless steel, CF3M
- Window material: glass

### Cable entries/cable glands



A0028352


24 Possible cable entries/cable glands

- 1 Internal thread M20 × 1.5
- 2 Cable gland M20 × 1.5
- 3 Adapter for cable entry with internal thread G ½" or NPT ½"
- 4 Device plug

Order code for "Housing", option B "GT18 dual compartment, 316L, compact" option K "GT18 dual compartment, 316L, remote"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	<ul style="list-style-type: none"> <li>Non-hazardous area</li> <li>Ex ia</li> <li>Ex ic</li> <li>Ex nA, Ex ec</li> <li>Ex tb</li> </ul>	Stainless steel ,1.4404
Adapter for cable entry with internal thread G ½"	Non-hazardous area and hazardous area (except for XP)	Stainless steel, 1.4404 (316L)
Adapter for cable entry with internal thread NPT ½"	Non-hazardous area and hazardous area	

Order code for "Housing": option C "GT20 dual compartment, aluminum, coated, compact", option J "GT20 dual compartment, aluminum, coated remote"

 Applies also to the following device versions in combination with HART communication mode: Order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam; 316L; 316L", option DB "Mass gas/liquid; 316L; 316L"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	<ul style="list-style-type: none"> <li>Non-hazardous area</li> <li>Ex ia</li> <li>Ex ic</li> </ul>	Plastic
	Adapter for cable entry with internal thread G ½"	Nickel-plated brass
Adapter for cable entry with internal thread NPT ½"	Non-hazardous area and hazardous area (except for XP)	Nickel-plated brass
Thread NPT ½" via adapter	Non-hazardous area and hazardous area	

#### Connecting cable for remote version

- Standard cable: PVC cable with copper shield
- Reinforced cable: PVC cable with copper shield and additional steel wire braided jacket

#### Connecting cable, pressure measuring cell

 For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:

- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.

Standard cable: PVC cable with copper shield

#### Sensor connection housing

The material of the sensor connection housing is dependent on the material selected for the transmitter housing.

- Order code for "Housing" option J "GT20 two-chamber, aluminum, coated, remote": Coated aluminum AlSi10Mg
- Order code for "Housing", option K "GT18 two-chamber, 316L, remote": Stainless cast steel, 1.4408 (CF3M)  
Compliant with:
  - NACE MR0175
  - NACE MR0103

**Measuring tubes**

**DN 25R to 200R (1R to 8R)/DN 40S to 250S (1½S to 10S"), pressure ratings PN 10/16/25/40, Class 150/300, and JIS 10K/20K**

- Stainless cast steel, CF3M/1.4408
- Complies with:
  - NACE MR0175-2003
  - NACE MR0103-2003
- DN15 to 150 (½ to 6"): AD2000, permitted temperature range -10 to +400 °C (+14 to +752 °F) restricted

**DSC sensor**

Order code for "Sensor version; DSC sensor; measuring tube", option **AA, BA, CA, DA, DB**

**Pressure ratings PN 10/16/25/40, Class 150/300, as well as JIS 10K/20K:**

Parts in contact with medium (marked as "wet" on the DSC sensor flange):

- Stainless steel 1.4404 and 316 and 316L
- Compliant with:
  - NACE MR0175/ISO 15156-2015
  - NACE MR0103/ISO 17945-2015

Parts not in contact with medium:

Stainless steel 1.4301 (304)

Order code for "Sensor version; DSC sensor; measuring tube", option **AB, BB, CB**

**Pressure ratings PN 10/16/25/40, Class 150/300, as well as JIS 10K/20K:**

Parts in contact with medium (marked as "wet" on the DSC sensor flange):

- Alloy C22, UNS N06022 similar to Alloy C22/2.4602
- Compliant with:
  - NACE MR0175/ISO 15156-2015
  - NACE MR0103/ISO 17945-2015

Parts not in contact with medium:

Alloy C22, UNS N06022 similar to Alloy C22/2.4602

**Pressure measuring cell**

For order code for "Sensor version; DSC sensor; measuring tube", option DA "Mass steam" and DB "Mass gas/liquid", the following applies:

- Only available for measuring instruments with the following communication protocols:
  - HART
  - PROFINET over Ethernet-APL
- Oil-free or grease-free cleaning is not possible.
- Wetted parts:
  - Process connection  
Stainless steel, 1.4404/316L
  - Membrane  
Stainless steel, 1.4435/316L
- Non-wetted parts:
  - Housing  
Stainless steel, 1.4404

Order code for "Sensor version; DSC sensor; measuring tube", option **DA, DB**

- Connection on meter body: Stainless steel, 1.4404/316/316L
- Connection on siphon <sup>4)</sup>: Stainless steel, 316/316L  
Siphon: Stainless steel, 1.4571
- Clamping sleeve: Stainless steel: 1.4571 (316Ti)
- Seals on meter body siphon: Sigraflex foil Z TM (BAM-certified (Federal Institute for Materials Research and Testing) for oxygen applications)
- Manometer valve:
  - PTFE (polytetrafluoro-ethylene)
  - Stainless steel, 1.4571 <sup>5)</sup>
- Pressure measuring cell manometer valve: Copper

4) Only available with order code for "Sensor version; DSC sensor; measuring tube", option DA.

5) Only for the order code for "Additional approval", option LV IBR: 316Ti

**Process connections**

**DN 25R to 200R (1R to 8R)/DN 40S to 250S (1½S to 10S), pressure ratings PN 10/16/25/40, Class 150/300, as well as JIS 10K/20K:**

- "R-type" with single inner diameter line size reduction: 25R to 200R (1R to 8R)  
Compliant with:
  - NACE MR0175-2003
  - NACE MR0103-2003
- "S-type" with double inner diameter line size reduction: DN 40S to 250S (1½S to 10S)  
Compliant with:
  - NACE MR0175-2003
  - NACE MR0103-2003

The following materials are available depending on the pressure rating:  
Stainless steel, multiple certifications, 1.4404/F316/F316L)



Available process connections → 94

**Seals**

- Graphite  
Sigraflex foil Z<sup>TM</sup> (BAM-certified for oxygen applications)
- FPM (Viton<sup>TM</sup>)
- Kalrez 6375<sup>TM</sup>
- Gylon 3504<sup>TM</sup> (BAM-certified for oxygen applications)

Order code for "Sensor version; DSC sensor; measuring tube", option DA, DB  
Copper



The technical tightness of tightness class L0.01 according to the TA-Luft regulation (Technical Instructions on Air Quality Control of December 1, 2021; Section 5.2.6.3 Flange connections), with a corresponding specific leakage rate of less than 0.01 mg/(s·m) was verified by means of type-based component tests at a test pressure of 40 bar<sub>a</sub>.

**Housing support**

Stainless steel, 1.4408 (CF3M)

**Screws for DSC sensor**

- Order code for "Sensor version", option AA "Stainless steel, A4-80 according to ISO 3506-1 (316)"
- Order code for "Sensor version", option BA, CA, DA, DB  
Stainless steel, A2 as per ISO 3506-1 (304)
- Order code for "Additional approval", option LL "AD 2000 (including option JA+JB+JK) > DN25 including option LK"  
Stainless steel, A4 as per ISO 3506-1 (316)
- Order code for "Sensor version", option AB, AC, BB, CB, CC  
Stainless steel, 1.4980 according to EN 10269 (Gr. 660 B)

**Accessories***Protective cover*

Stainless steel, 1.4404 (316L)

*Flow conditioner*

- Stainless steel, multiple certifications, 1.4404 (316, 316L)
- Compliant with:
  - NACE MR0175-2003
  - NACE MR0103-2003

**Flange connections**

Flange connection dimensions and raised face in accordance with:

- DIN EN 1092-1
- ASME B16.5
- JIS B2220









For information on the different materials used in the process connections

# Operability

Operating concept	<p><b>Operator-oriented menu structure for user-specific tasks</b></p> <ul style="list-style-type: none"><li>■ Commissioning</li><li>■ Operation</li><li>■ Diagnostics</li><li>■ Expert level</li></ul> <p><b>Quick and safe commissioning</b></p> <ul style="list-style-type: none"><li>■ Guided menus ("Make-it-run" wizards) for applications</li><li>■ Menu guidance with brief descriptions of the individual parameter functions</li></ul> <p><b>Reliable operation</b></p> <ul style="list-style-type: none"><li>■ Operation in the following languages:<ul style="list-style-type: none"><li>■ Via local display: English, German, French, Spanish, Italian, Portuguese, Polish, Russian, Turkish, Chinese, Bahasa (Indonesian)</li><li>■ Via "FieldCare" operating tool: English, German, French, Spanish, Italian, Chinese</li></ul></li><li>■ Uniform operating philosophy applied to device and operating tools</li><li>■ If replacing the electronic module, transfer the device configuration via the integrated memory (integrated HistoROM) which contains the process and measuring device data. No need to reconfigure.</li></ul> <p><b>Efficient diagnostic behavior increases measurement availability</b></p> <ul style="list-style-type: none"><li>■ Troubleshooting measures can be called up via the device and in the operating tools</li><li>■ Diverse simulation options for events that occur and optional line recorder functions</li></ul>
-------------------	--

Languages	<p>Can be operated in the following languages:</p> <ul style="list-style-type: none"><li>■ Via local display: English, German, French, Spanish, Italian, Portuguese, Polish, Russian, Turkish, Chinese, Bahasa (Indonesian)</li><li>■ Via "FieldCare" operating tool: English, German, French, Spanish, Italian, Chinese</li></ul>
-----------	--

Onsite operation	<p><b>Via display module</b></p> <p>Two display modules are available:</p> <table><tr><th>Order code for "Display; Operation", option C "SD02"</th><th>Order code for "Display; Operation", option E "SD03"</th></tr><tr><td> <small>A0032219</small></td><td> <small>A0032221</small></td></tr><tr><td>1    Operation with pushbuttons</td><td>1    Operation with touch control</td></tr></table>	Order code for "Display; Operation", option C "SD02"	Order code for "Display; Operation", option E "SD03"	 <small>A0032219</small>	 <small>A0032221</small>	1    Operation with pushbuttons	1    Operation with touch control
Order code for "Display; Operation", option C "SD02"	Order code for "Display; Operation", option E "SD03"						
 <small>A0032219</small>	 <small>A0032221</small>						
1    Operation with pushbuttons	1    Operation with touch control						

Display elements

- 4-line, illuminated, graphic display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured

*Operating elements*


- Operation with 3 push buttons with open housing: ⊕, ⊖, ⊞  
or
- External operation via touch control (3 optical keys) without opening the housing: ⊕, ⊖, ⊞
- Operating elements also accessible in the various zones of the hazardous area

*Additional functionality*

- Data backup function  
The device configuration can be saved in the display module.
- Data comparison function  
The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function  
The transmitter configuration can be transmitted to another device using the display module.

**Via remote display FHX50**

- The remote display FHX50 can be ordered as an optional extra → 104.
- The remote display FHX50 cannot be combined with the order code for "Sensor version; DSC sensor; measuring tube", option DA "mass steam" or option DB "mass gas/liquid".



A0032215

25 FHX50 operating options

- 1 SD02 display and operating module, push buttons: cover must be opened for operation
- 2 SD03 display and operating module, optical buttons: operation possible through cover glass


*Display and operating elements*

The display and operating elements correspond to those of the display module .

**Remote operation****Via HART protocol**

This communication interface is available in device versions with a HART output.






A0028746

26 Options for remote operation via HART protocol (passive)

- 1 Automation system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with Web browser (e.g. Internet Explorer) for accessing computers with an operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, AMS TREX Device Communicator, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 Field Xpert SMT50 (or 70 or 77)
- 9 VIATOR Bluetooth modem with connecting cable
- 10 Transmitter

### Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.




A0028838

27 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Segment coupler PROFIBUS DP/PA
- 5 PROFIBUS PA network
- 6 T-box
- 7 Measuring instrument

### Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




A0028837

28 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- 3 Industry network
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring instrument

## Service interface


### Via service interface (CDI)



A0034056

- 1 Service interface (CDI = Endress+Hauser Common Data Interface) of the measuring instrument
- 2 Commubox FXA291
- 3 Computer with operating tool (e.g. FieldCare or DeviceCare) and (CDI) DeviceDTM

Via PROFINET over Ethernet-APL/SPE 10 Mbit/s



A0046859

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet Switch, e.g. Scalance X204 (Siemens)
- 3 Computer with operating tool (e.g. FieldCare or DeviceCare) and (CDI) DeviceDTM
- 4 Ethernet cable with RJ45 plug
- 5 APL field switch
- 6 2-wire fieldbus cable type A
- 7 Measuring instrument

Supported operating tools

Different operating tools can be used for local or remote access to the measuring device. Depending on the operating tool used, access is possible with different operating units and via a variety of interfaces.

Supported operating tools	Operating unit	Interface	Additional information
DeviceCare SFE100	Notebook, PC or tablet with Microsoft Windows system	CDI service interface	→ 106
FieldCare SFE500	Notebook, PC or tablet with Microsoft Windows system	CDI service interface	→ 106
Field Xpert	SMT70/77/50	CDI service interface	Operating Instructions BA01202S Device description files: Use update function of handheld terminal



- Other operating tools based on FDT technology with a device driver such as DTM/iDTM or DD/EDD can be used for device operation. These operating tools are available from the individual manufacturers. Integration into the following operating tools, among others, is supported:
- FactoryTalk AssetCentre (FTAC) from Rockwell Automation → [www.rockwellautomation.com](http://www.rockwellautomation.com)
  - Process Device Manager (PDM) from Siemens → [www.siemens.com](http://www.siemens.com)
  - Asset Management Solutions (AMS) from Emerson → [www.emersonprocess.com](http://www.emersonprocess.com)
  - FieldCommunicator 375/475 from Emerson → [www.emersonprocess.com](http://www.emersonprocess.com)
  - Emersons TREX → [www.emerson.com](http://www.emerson.com)
  - Field Device Manager (FDM) from Honeywell → [www.process.honeywell.com](http://www.process.honeywell.com)
  - FieldMate from Yokogawa → [www.yokogawa.com](http://www.yokogawa.com)
  - PACTWare → [www.pactware.com](http://www.pactware.com)

The related device description files are available: [www.endress.com](http://www.endress.com) → Download Area

### Web server

With the integrated Web server, the device can be operated and configured via a Web browser and PROFINET over Ethernet-APL. In addition to the measured values, status information on the device is displayed and can be used to monitor device health. Furthermore the device data can be managed and the network parameters can be configured.

Access to the network is required for the APL connection.

#### Supported functions

Data exchange between the operating unit (such as a notebook for example) and the measuring instrument:

- Upload the configuration from the measuring instrument (XML format, configuration backup)
- Save the configuration to the measuring instrument (XML format, restore configuration)
- Export parameter settings (.csv file or PDF file, document the measuring point configuration)
- Export the Heartbeat verification log (PDF file, only available with the "Heartbeat Verification" application package)
- Download driver (GSD) for system integration





Special Documentation for Web server

## Certificates and approvals

Current certificates and approvals for the product are available at [www.endress.com](http://www.endress.com) on the relevant product page:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Downloads**.

<b>CE mark</b>	<p>The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.</p> <p>Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.</p>
<b>UKCA marking</b>	<p>The device meets the legal requirements of the applicable UK regulations (Statutory Instruments). These are listed in the UKCA Declaration of Conformity along with the designated standards. By selecting the order option for UKCA marking, Endress+Hauser confirms a successful evaluation and testing of the device by affixing the UKCA mark.</p> <p>Contact address Endress+Hauser UK: Endress+Hauser Ltd. Floats Road Manchester M23 9NF United Kingdom <a href="http://www.uk.endress.com">www.uk.endress.com</a></p>
<b>RCM marking</b>	<p>The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".</p>
<b>Ex approval</b>	<p>The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.</p> <p> The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.</p>
<b>Functional safety</b>	<p>The measuring instrument can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture; order code for "Additional approval", option LA) and SIL 3 (multi-channel architecture with homogeneous redundancy) and is independently evaluated and certified in accordance with IEC 61508.</p> <p>The following types of monitoring in safety equipment are possible:</p> <p> Functional safety manual with information for the SIL device</p>

<b>HART certification</b>	<b>HART interface</b> <p>The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:</p> <ul style="list-style-type: none"> <li>■ Certified according to HART</li> <li>■ The device can also be operated with certified devices of other manufacturers (interoperability)</li> </ul>
<b>FOUNDATION Fieldbus certification</b>	<b>FOUNDATION Fieldbus interface</b> <p>The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:</p> <ul style="list-style-type: none"> <li>■ Certified in accordance with FOUNDATION Fieldbus H1</li> <li>■ Interoperability Test Kit (ITK), revision version 6.2.0 (certificate available on request)</li> <li>■ Physical Layer Conformance Test</li> <li>■ The device can also be operated with certified devices of other manufacturers (interoperability)</li> </ul>
<b>Certification PROFIBUS</b>	<b>PROFIBUS interface</b> <p>The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V./ PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:</p> <ul style="list-style-type: none"> <li>■ Certified according to PA Profile 3.02</li> <li>■ The device can also be operated with certified devices of other manufacturers (interoperability)</li> </ul>
<b>PROFINET over Ethernet-APL certification</b>	<b>PROFINET interface</b> <p>The measuring instrument is certified and registered by the PROFIBUS Nutzerorganisation e.V. (PNO). The measuring system meets all the requirements of the following specifications:</p> <ul style="list-style-type: none"> <li>■ Certified according to: <ul style="list-style-type: none"> <li>■ Test specification for PROFINET devices</li> <li>■ PROFINET PA Profile 4.02</li> <li>■ PROFINET Netload Robustness Class 2 10 Mbit/s</li> <li>■ APL conformance test</li> </ul> </li> <li>■ The device can also be operated with certified devices of other manufacturers (interoperability)</li> <li>■ The device supports PROFINET S2 system redundancy.</li> </ul>
<b>Pressure Equipment Directive</b>	<p>The measuring devices can be ordered with or without PED or PESR. If a device with PED or PESR is required, this must be ordered explicitly. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary. A UK order option must be selected for PESR under the order code for "Approvals".</p> <ul style="list-style-type: none"> <li>■ With the marking <ul style="list-style-type: none"> <li>a) PED/G1/x (x = category) or</li> <li>b) PESR/G1/x (x = category)</li> </ul> <p>on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements"</p> <ul style="list-style-type: none"> <li>a) specified in Annex I of the Pressure Equipment Directive 2014/68/EU or</li> <li>b) Schedule 2 of Statutory Instruments 2016 No. 1105.</li> </ul> </li> <li>■ Devices bearing this marking (PED or PESR) are suitable for the following types of medium: Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to 0.5 bar (7.3 psi)</li> <li>■ Devices not bearing this marking (without PED or PESR) are designed and manufactured according to sound engineering practice. They meet the requirements of <ul style="list-style-type: none"> <li>a) Art. 4 Para. 3 of the Pressure Equipment Directive 2014/68/EU or</li> <li>b) Part 1, Para. 8 of Statutory Instruments 2016 No. 1105.</li> </ul> <p>The scope of application is indicated</p> <ul style="list-style-type: none"> <li>a) in diagrams 6 to 9 in Annex II of the Pressure Equipment Directive 2014/68/EU or</li> <li>b) Schedule 3, Para. 2 of Statutory Instruments 2016 No. 1105.</li> </ul> </li> </ul>
<b>Experience</b>	<p>The Prowirl 200 measuring system is the successor model of the Prowirl 72 and Prowirl 73.</p>

## External standards and guidelines

- EN 60529  
Degrees of protection provided by enclosure (IP code)
- DIN ISO 13359  
Measurement of conductive liquid flow in closed conduits - Flanged-type electromagnetic flowmeters - Overall length
- ISO 12764:2017  
Measurement of fluid flow in closed conduits – Flow rate measurement by means of vortex shedding flowmeters inserted in circular cross-section conduits running full
- EN 61010-1  
Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements
- EN 61326-1/-2-3  
EMC requirements for electrical equipment for measurement, control and laboratory use
- NAMUR NE 21  
Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment
- NAMUR NE 32  
Data retention in the event of a power failure in field and control instruments with microprocessors
- NAMUR NE 43  
Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.
- NAMUR NE 53  
Software of field devices and signal-processing devices with digital electronics
- NAMUR NE 105  
Specifications for integrating fieldbus devices in engineering tools for field devices
- NAMUR NE 107  
Self-monitoring and diagnosis of field devices
- NAMUR NE 131  
Requirements for field devices for standard applications
- ETSI EN 300 328  
Guidelines for 2.4 GHz radio components.
- EN 301489  
Electromagnetic compatibility and radio spectrum matters (ERM).

## Ordering information

Detailed ordering information is available from your nearest sales organization [www.addresses.endress.com](http://www.addresses.endress.com) or in the Product Configurator at [www.endress.com](http://www.endress.com):

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Configuration**.



### Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: direct input of information specific to the measuring point, such as the measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

## Product generation index

Release date	Product root	Change
01.09.2013	7R2B	TI01086D
01.11.2017	7R2C	TI01335D
01.09.2025	7R2C	TI01335D




More information is available from your Sales Center or at:  
[www.service.endress.com](http://www.service.endress.com) → Downloads

## Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: [www.endress.com](http://www.endress.com).



Detailed information on the application packages:  
Special Documentation →  108

---

### Diagnostic functionality

Order code for "Application package", option EA "Extended HistoROM"

Comprises extended functions concerning the event log and the activation of the measured value memory.

Event log:

Memory volume is extended from 20 message entries (standard version) to up to 100 entries.

Data logging (line recorder):

- Memory capacity for up to 1000 measured values is activated.
- 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user.
- Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server.



For detailed information, see the Operating Instructions for the device.

---

### Heartbeat Technology

Order code for "Application package", option EB "Heartbeat Verification"


#### Heartbeat Verification

Meets the requirement for traceable verification in accordance with DIN ISO 9001:2008

Clause 7.6 a) "Control of monitoring and measuring equipment".

- Functional testing in the installed state without interrupting the process.
- Traceable verification results on request, including a report.
- Simple testing process via local operation or other operating interfaces.
- Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.
- Extension of calibration intervals according to operator's risk assessment.








Detailed information on Heartbeat Technology:  
Special Documentation →  108

## Accessories


Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: [www.endress.com](http://www.endress.com).

## Device-specific accessories


## For the transmitter

Accessories	Description
Prowirl 200 transmitter	<p>Transmitter for replacement or storage. Use the order code to define the following specifications:</p> <ul style="list-style-type: none"> <li>■ Approvals</li> <li>■ Output, input</li> <li>■ Display/operation</li> <li>■ Housing</li> <li>■ Software</li> </ul> <p> Installation Instructions EA01056D</p> <p> (Order number: 7X2CXX)</p>
Remote display FHX50	<p>FHX50 housing for accommodating a display module .</p> <ul style="list-style-type: none"> <li>■ FHX50 housing suitable for: <ul style="list-style-type: none"> <li>■ SD02 display module (push buttons)</li> <li>■ SD03 display module (touch control)</li> </ul> </li> <li>■ Length of connecting cable: up to max. 60 m (196 ft) (cable lengths available for order: 5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft))</li> </ul> <p>The measuring instrument can be ordered with the FHX50 housing and a display module. The following options must be selected in the separate order codes:</p> <ul style="list-style-type: none"> <li>■ Order code for measuring instrument, feature 030: Option L or M "Prepared for FHX50 display"</li> <li>■ Order code for FHX50 housing, feature 050 (device version): Option A "Prepared for FHX50 display"</li> <li>■ Order code for FHX50 housing, depends on the desired display module in feature 020 (display, operation): <ul style="list-style-type: none"> <li>■ Option C: for an SD02 display module (push buttons)</li> <li>■ Option E: for an SD03 display module (touch control)</li> </ul> </li> </ul> <p>The FHX50 housing can also be ordered as a retrofit kit. The measuring instrument display module is used in the FHX50 housing. The following options must be selected in the order code for the FHX50 housing:</p> <ul style="list-style-type: none"> <li>■ Feature 050 (measuring instrument version): option B "Not prepared for FHX50 display"</li> <li>■ Feature 020 (display, operation): option A "None, existing displayed used"</li> </ul> <p> The FHX50 remote display cannot be combined with the order code for "Sensor version; DSC sensor; measuring tube":</p> <ul style="list-style-type: none"> <li>■ option DA "Mass steam; 316L; 316L (integrated pressure/temperature measurement), -200 to +400 °C (-328 to +750 °F)"</li> <li>■ option DB "Mass gas/liquid; 316L; 316L (integrated pressure/temperature measurement), -40 to +100 °C (-40 to +212 °F)"</li> </ul> <p> Special Documentation SD01007F</p> <p>(Order number: FHX50)</p>
Overvoltage protection for 2-wire devices	<p>Ideally, the overvoltage protection module should be ordered directly with the device. See product structure, feature 610 "Accessory mounted", option NA "Overvoltage protection". Separate order necessary only if retrofitting.</p> <ul style="list-style-type: none"> <li>■ OVP10: For 1-channel devices (feature 020, option A):</li> <li>■ OVP20: For 2-channel devices (feature 020, options B, C, E or G)</li> </ul> <p> Special Documentation SD01090F</p> <p>(Order number OVP10: 71128617) (Order number OVP20: 71128619)</p>
Overvoltage protection for 2-wire devices	<p>The use of an external overvoltage protection, e.g. HAW 569, is recommended.</p>











Accessories	Description
Protective cover	<p>The protective cover is used to protect against direct sunlight, precipitation and ice. It can be ordered together with the device via the product structure: Order code for "Accessories enclosed" option PB "Protective cover"</p> <p> Special Documentation SD00333F</p> <p>(Order number: 71162242)</p>
Transmitter holder (pipe mounting)	<p>To secure the remote version to the pipe DN 20 to 80 (3/4 to 3") Order code for "Accessory enclosed", option PM</p>

**For the sensor**



Accessories	Description
Flow conditioner	<p>Is used to shorten the necessary inlet run. (Order number: DK7ST)</p> <p> Dimensions of flow conditioner</p>

**Communication-specific accessories**




Accessories	Description
Commubox FXA195 HART	<p>For intrinsically safe HART communication with FieldCare via the USB interface.</p> <p> Technical Information TI00404F</p>
Commubox FXA291	<p>Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop.</p> <p> Technical Information TI00405C</p>
HART loop converter HMX50	<p>Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.</p> <p> <ul style="list-style-type: none"> <li>Technical Information TI00429F</li> <li>Operating Instructions BA00371F</li> </ul> </p>
Wireless HART adapter SWA70	<p>Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity.</p> <p> Operating Instructions BA00061S</p>
Fieldgate FXA42	<p>Transmission of the measured values of connected 4 to 20 mA analog measuring instruments, as well as digital measuring instruments</p> <p> <ul style="list-style-type: none"> <li>Technical Information TI01297S</li> <li>Operating Instructions BA01778S</li> <li>Product page: <a href="http://www.endress.com/fxa42">www.endress.com/fxa42</a></li> </ul> </p>
Field Xpert SMT50	<p>The Field Xpert SMT50 tablet PC for device configuration enables mobile plant asset management in non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.</p> <p> <ul style="list-style-type: none"> <li>Technical Information TI01555S</li> <li>Operating Instructions BA02053S</li> <li>Product page: <a href="http://www.endress.com/smt50">www.endress.com/smt50</a></li> </ul> </p>

Field Xpert SMT70	<p>The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress.</p> <p>This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.</p> <p> <ul style="list-style-type: none"> <li>■ Technical Information TI01342S</li> <li>■ Operating Instructions BA01709S</li> <li>■ Product page: <a href="http://www.endress.com/smt70">www.endress.com/smt70</a></li> </ul> </p>
Field Xpert SMT77	<p>The Field Xpert SMT77 tablet PC for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1.</p> <p> <ul style="list-style-type: none"> <li>■ Technical Information TI01418S</li> <li>■ Operating Instructions BA01923S</li> <li>■ Product page: <a href="http://www.endress.com/smt77">www.endress.com/smt77</a></li> </ul> </p>

## Service-specific accessories

Accessories	Description
Applicator	<p>Software for selecting and sizing Endress+Hauser measuring instruments:</p> <ul style="list-style-type: none"> <li>■ Choice of measuring instruments for industrial requirements</li> <li>■ Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy.</li> <li>■ Graphic display of the calculation results</li> <li>■ Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.</li> </ul> <p>Applicator is available: Via the Internet: <a href="https://portal.endress.com/webapp/applicator">https://portal.endress.com/webapp/applicator</a></p>
Netilion	<p>IIoT ecosystem: Unlock knowledge</p> <p>With the Netilion IIoT ecosystem, Endress+Hauser allows you to optimize your plant performance, digitize workflows, share knowledge, and enhance collaboration.</p> <p>Drawing upon decades of experience in process automation, Endress+Hauser offers the process industry an IIoT ecosystem designed to effortlessly extract insights from data. These insights allow process optimization, leading to increased plant availability, efficiency, and reliability - ultimately resulting in a more profitable plant.</p> <p><a href="http://www.netilion.endress.com">www.netilion.endress.com</a></p>
FieldCare	<p>FDT-based plant asset management tool from Endress+Hauser.</p> <p>It can configure all intelligent field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.</p> <p> Operating Instructions BA00027S and BA00059S</p>
DeviceCare	<p>Tool to connect and configure Endress+Hauser field devices.</p> <p> Innovation brochure IN01047S</p>

## System components

Accessories	Description
Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.  <ul style="list-style-type: none"> <li>■ Technical Information TI00133R</li> <li>■ Operating Instructions BA00247R</li> </ul>
RN221N	Active barrier with power supply for safe separation of 4-20 mA standard signal circuits. Offers bidirectional HART transmission.  <ul style="list-style-type: none"> <li>■ Technical Information TI00073R</li> <li>■ Operating Instructions BA00202R</li> </ul>
RNS221	Supply unit for powering two 2-wire measuring devices solely in the non-hazardous area. Bidirectional communication is possible via the HART communication jacks.  <ul style="list-style-type: none"> <li>■ Technical Information TI00081R</li> <li>■ Brief Operating Instructions KA00110R</li> </ul>

## Documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- *Device Viewer* ([www.endress.com/deviceviewer](http://www.endress.com/deviceviewer)): Enter the serial number from the nameplate
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

## Standard documentation



Supplementary information on the semi-standard options is available in the relevant Special Documentation in the TSP database.

## Brief Operating Instructions

*Brief Operating Instructions for the sensor*

Measuring device	Documentation code
Prowirl R 200	KA01325D

*Brief Operating Instructions for the transmitter*

Measuring instrument	Documentation code			
	HART	FOUNDATION Fieldbus	PROFIBUS PA	PROFINET over Ethernet-APL
Proline 200	KA01326D	KA01327D	KA01328D	KA01323D

## Operating Instructions

Measuring instrument	Documentation code				
	HART	FOUNDATION Fieldbus	PROFIBUS PA	PROFINET over Ethernet-APL	Modbus TCP over Ethernet-APL
Prowirl R 200	BA01688D	BA01696D	BA01692D	BA02135D	BA02400D

## Description of Device Parameters

Measuring instrument	Documentation code			
	HART	FOUNDATION Fieldbus	PROFIBUS PA	PROFINET over Ethernet-APL
Prowirl 200	GP01109D	GP01111D	GP01110D	GP01170D

## Supplementary device-dependent documentation

## Safety instructions

Contents	Documentation code
ATEX/IECEX Ex d	XA01635D
ATEX/IECEX Ex ia	XA01636D
ATEX/IECEX Ex ec, Ex ic	XA01637D
cCSA <sub>US</sub> XP	XA01638D
cCSA <sub>US</sub> IS	XA01639D
EAC Ex d	XA01684D
EAC Ex ia	XA01782D
EAC Ex ec, Ex ic	XA01685D
INMETRO Ex d	XA01642D
INMETRO Ex ia	XA01640D
INMETRO Ex ec, Ex ic	XA01641D
JPN Ex d	XA01766D
NEPSI Ex d	XA01643D
NEPSI Ex ia	XA01644D
NEPSI Ex ec, Ex ic	XA01645D
UKEX Ex d	XA02630D
UKEX Ex ia	XA02631D
UKEX Ex ec, Ex ic	XA02632D

## Functional Safety Manual


Contents	Documentation code
Proline Prowirl 200	SD02025D

## Special Documentation

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01614D
Protective cover	SD00333F

Contents	Documentation code			
	HART	FOUNDATION Fieldbus	PROFIBUS PA	PROFINET over Ethernet-APL
Heartbeat Technology	SD02029D	SD02030D	SD02031D	SD02759D
Web server	–	–	–	SD02834D

**Installation Instructions**

Contents	Note
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory →  104.

**Registered trademarks****HART®**

Registered trademark of the FieldComm Group, Austin, Texas USA

**PROFIBUS®**

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

**FOUNDATION™ Fieldbus**

Registration-pending trademark of the FieldComm Group, Austin, Texas, USA

**Ethernet-APL™**

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

**KALREZ®, VITON®**

Registered trademarks of DuPont Performance Elastomers L.L.C., Wilmington, DE USA

**GYLON®**

Registered trademark of Garlock Sealing Technologies, Palmyra, NY, USA



[www.addresses.endress.com](http://www.addresses.endress.com)

---