

Technical Information

Proline Promag W 10

Electromagnetic flowmeter



Flowmeter for basic water and wastewater applications with easy-to-use operation concept

Application

- The bidirectional measuring principle is virtually independent of pressure, density, temperature and viscosity
- Suitable for basic measuring tasks such as raw water infeed

Device properties

- International drinking water approvals
- Degree of protection IP68 (Type 6P enclosure)
- System integration with HART, Modbus RS485, IO-Link
- Flexible operation with app and optional display

Your benefits

- Reliable measurement at constant accuracy with 0 x DN run without pressure loss
- Flexible engineering – sensor with fixed or lap-joint process connections
- Application suitability – EN ISO 12944 corrosion protection for underground or underwater installation
- Improved plant availability – sensor compliant with industry-specific requirements
- Optimum usability – operation with mobile devices and SmartBlue app or display with touchscreen
- Simple, time-saving commissioning – guided parameterization in advance and in the field
- Built-in verification – Heartbeat Technology

Table of contents

About this document	6	Vibration resistance and shock resistance	55
Symbols	6	Electromagnetic compatibility (EMC)	55
Related documentation	6		
Ordering information	6		
Registered trademarks	8		
Function and system design	10	Process	58
Measuring principle	10	Medium temperature range	58
Product design	10	Conductivity	58
IT security	11	Flow limit	58
Device-specific IT security	12	Pressure/temperature ratings	60
		Pressure tightness	63
		Pressure loss	63
Input	14	Mechanical construction	66
Measured variable	14	Weight	66
Operable flow range	14	Measuring tube specification in SI units	69
Measuring range	14	Measuring tube specification in US units	70
		Materials	72
Output	20	Fitted electrodes	73
Output versions	20	Process connections	73
Output signal	20	Surface roughness	73
Signal on alarm	23		
Low flow cut off	23	Dimensions in SI units	76
Galvanic isolation	23	Compact version	76
Protocol-specific data	24	Remote version	82
		Fixed flange	87
Power supply	28	Lap joint flange	98
Terminal assignment	28	Lap joint flange, stamped plate	101
Supply voltage	28	Accessories	102
Power consumption	29		
Current consumption	29	Dimensions in US units	106
Power supply failure	29	Compact version	106
Electrical connection	29	Remote version	112
Potential equalization	33	Fixed flange	117
Terminals	35	Lap joint flange	119
Cable entries	35	Accessories	120
Overvoltage protection	36		
Cable specifications	38	Local display	124
Requirements for connecting cable	38	Operation concept	124
Ground cable requirements	38	Operation options	125
Connecting cable requirements	38	Operating tools	125
Performance characteristics	42	Certificates and approvals	128
Reference operating conditions	42	Non-Ex approval	128
Maximum measurement error	42	Pressure Equipment Directive	128
Repeatability	43	Drinking water approval	128
Influence of ambient temperature	43	Pharmaceutical compatibility	128
		HART certification	128
Installation	46	Radio approval	128
Installation conditions	46	Additional approvals	128
		Additional certification	128
		External standards and guidelines	128
Environment	54	Application packages	132
Ambient temperature range	54	Use	132
Storage temperature	54	Heartbeat Verification + Monitoring	132
Relative humidity	54		
Operating height	54	Accessories	134
Atmosphere	54	Device-specific accessories	134
Degree of protection	54	Communication-specific accessories	135





Service-specific accessory	136
System components	136

About this document



Symbols	6
Related documentation	6
Ordering information	6
Registered trademarks	8

Symbols








Electronics

-  Direct current
-  Alternating current
-  Direct current and alternating current
-  Terminal connection for potential equalization



Device communication

-  Communication via a wireless, local area network.
-  Bluetooth is enabled.

Types of information


-  Preferred procedures, processes or actions
-  Permitted procedures, processes or actions
-  Forbidden procedures, processes or actions
-  Additional information
-  Reference to documentation
-  Reference to page
-  Reference to graphic

Explosion protection

-  Hazardous area
-  Non-hazardous area

Related documentation

Technical information	Overview of the device with the most important technical data.
Operating instructions	All the information that is required in the various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal as well as the technical data and dimensions.
Sensor Brief Operating Instructions	Incoming acceptance, transport, storage and mounting of the device.
Transmitter Brief Operating Instructions	Electrical connection and commissioning of the device.
Description of Parameters	Detailed explanation of the menus and parameters.
Safety Instructions	Documents for the use of the device in hazardous areas.
Special Documentation	Documents with more detailed information on specific topics.
Installation Instructions	Installation of spare parts and accessories.

-  The device documentation is available online on the device product page and in the Downloads area: www.endress.com

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

1. Select the product using the filters and search field.

2. Open the product page.

3. Select **Configuration**.



Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: direct input of information specific to the measuring point, such as the measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas USA

Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

IO-Link®

Is a registered trademark. It may only be used in conjunction with products and services by members of the IO-Link Community or by non-members who hold an appropriate license. For more specific guidelines on use, refer to the IO-Link Community rules on: www.io-link.com.

Bluetooth®

The Bluetooth word mark and Bluetooth logos are registered trademarks of Bluetooth SIG. Inc. and any use of such marks by Endress+Hauser is under license. Other trademarks and trade names are those of their respective owners.

Apple®

Apple, the Apple logo, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc.

Android®


Android, Google Play and the Google Play logo are trademarks of Google Inc.

Function and system design

Measuring principle	10
Product design	10
IT security	11
Device-specific IT security	12

Measuring principle

According to *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



A0028962

- U_e Induced voltage
 B Magnetic induction (magnetic field)
 L Electrode spacing
 I Current
 v Flow velocity

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The induced voltage (U_e) is proportional to the flow velocity (v) and is transmitted to the amplifier via the working electrodes. The flow volume (Q) is calculated via the pipe cross-section (A). The DC magnetic field is generated by a switched direct current of alternating polarity.

Formulae for calculation

- Induced voltage $U_e = B \cdot L \cdot v$
- Volume flow $Q = A \cdot v$

Product design


The device consists of a transmitter and a sensor.

Two device versions are available:

- Compact version – transmitter and sensor form a mechanical unit.
- Remote version - transmitter and sensor are mounted in separate locations.

Compact version

The transmitter and sensor form a mechanical unit.




A0008262

- 1 Transmitter
 2 Sensor

Remote version






The transmitter and sensor are mounted in physically separate locations.



A0028196

- 1 Transmitter
- 2 Sensor connection housing
- 3 Sensor
- 4 Connecting cable

Measuring system

Proline 10 transmitter	Promag W sensor	
		
Compact version	DN 25 to 300 mm (1 to 12 in)	DN 25 to 300 mm (1 to 12 in)
		
Remote version	DN 350 to 3000 mm (14 to 120 in)	

IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

Device-specific IT security

Access via Bluetooth

Secure signal transmission via Bluetooth uses an encryption method tested by the Fraunhofer Institute.

- Without the SmartBlue App, the device is not visible via Bluetooth.
- Only one point-to-point connection is established between the device and a smartphone or tablet.

Access via the SmartBlue App

Two access levels (user roles) are defined for the device: the **Operator** user role and the **Maintenance** user role. The **Maintenance** user role is configured when the device leaves the factory.

If a user-specific access code is not defined (in the Enter access code parameter), the default setting **0000** continues to apply and the **Maintenance** user role is automatically enabled. The device's configuration data are not write-protected and can be edited at all times.

If a user-specific access code has been defined (in the Enter access code parameter), all the parameters are write-protected. The device is accessed with the **Operator** user role. When the user-specific access code is entered a second time, the **Maintenance** user role is enabled. All parameters can be written to.



For detailed information, see the "Description of Device Parameters" document pertaining to the device.

Protecting access via a password

There are a variety of ways to protect against write access to the device parameters:

- User-specific access code:
Protect write access to the device parameters via all the interfaces.
- Bluetooth key:
The password protects access and the connection between an operating unit, e.g. a smartphone or tablet, and the device via the Bluetooth interface.

General notes on the use of passwords

- The access code and Bluetooth key that are valid when the device is delivered must be redefined during commissioning.
- Follow the general rules for generating a secure password when defining and managing the access code and Bluetooth key.
- The user is responsible for the management and careful handling of the access code and Bluetooth key.

Write protection switch

The entire operating menu can be locked via the write protection switch. The values of the parameters cannot be changed. Write protection is disabled when the device leaves the factory.

Write protection is enabled with the write protection switch on the back of the display module.

Input

Measured variable	14
Operable flow range	14
Measuring range	14

Measured variable

Direct measured variables	<ul style="list-style-type: none"> ▪ Volume flow (proportional to induced voltage) ▪ Conductivity (order code for "Sensor option", option CX)
Calculated measured variables	Mass flow

Operable flow range

Over 1000 : 1

Measuring range

Typically $v = 0.01$ to 10 m/s (0.03 to 33 ft/s) with specified measuring accuracy

Electrical conductivity:

- ≥ 5 $\mu\text{S/cm}$ for liquids in general
- ≥ 20 $\mu\text{S/cm}$ for demineralized water

Flow characteristic values in SI units: DN 25 to 125 (1 to 4")

Nominal diameter		Recommended flow rate min./max. full scale value ($v \sim 0.3/10$ m/s)	Full scale value current output ($v \sim 2.5$ m/s)	Factory settings	
[mm]	[in]			Pulse value (~ 2 pulse/s)	Low flow cut off ($v \sim 0.04$ m/s)
		[dm ³ /min]	[dm ³ /min]	[dm ³]	[dm ³ /min]
25	1	9 to 300	75	0.5	1
32	–	15 to 500	125	1	2
40	1 ½	25 to 700	200	1.5	3
50	2	35 to 1100	300	2.5	5
65	–	60 to 2000	500	5	8
80	3	90 to 3000	750	5	12
100	4	145 to 4700	1200	10	20
125	–	220 to 7500	1850	15	30

Flow characteristic values in SI units: DN 150 to 3000 (6 to 120")

Nominal diameter		Recommended flow rate min./max. full scale value ($v \sim 0.3/10$ m/s)	Full scale value current output ($v \sim 2.5$ m/s)	Factory settings	
[mm]	[in]			Pulse value (~ 2 pulse/s)	Low flow cut off ($v \sim 0.04$ m/s)
		[m ³ /h]	[m ³ /h]	[m ³]	[m ³ /h]
150	6	20 to 600	150	0.025	2.5
200	8	35 to 1100	300	0.05	5
250	10	55 to 1700	500	0.05	7.5
300	12	80 to 2400	750	0.1	10
350	14	110 to 3300	1000	0.1	15
375	15	140 to 4200	1200	0.15	20
400	16	140 to 4200	1200	0.15	20
450	18	180 to 5400	1500	0.25	25
500	20	220 to 6600	2000	0.25	30
600	24	310 to 9600	2500	0.3	40

Nominal diameter		Recommended flow rate min./max. full scale value (v ~ 0.3/10 m/s)	Full scale value current output (v ~ 2.5 m/s)	Factory settings	
[mm]	[in]			[m ³ /h]	Pulse value (~ 2 pulse/s) [m ³]
700	28	420 to 13 500	3500	0.5	50
750	30	480 to 15 000	4000	0.5	60
800	32	550 to 18 000	4500	0.75	75
900	36	690 to 22 500	6000	0.75	100
1000	40	850 to 28 000	7000	1	125
-	42	950 to 30 000	8000	1	125
1200	48	1 250 to 40 000	10 000	1.5	150
-	54	1 550 to 50 000	13 000	1.5	200
1400	-	1 700 to 55 000	14 000	2	225
-	60	1 950 to 60 000	16 000	2	250
1600	-	2 200 to 70 000	18 000	2.5	300
-	66	2 500 to 80 000	20 500	2.5	325
1800	72	2 800 to 90 000	23 000	3	350
-	78	3 300 to 100 000	28 500	3.5	450
2000	-	3 400 to 110 000	28 500	3.5	450
-	84	3 700 to 125 000	31 000	4.5	500
2200	-	4 100 to 136 000	34 000	4.5	540
-	90	4 300 to 143 000	36 000	5	570
2400	-	4 800 to 162 000	40 000	5.5	650
-	96	5 000 to 168 000	42 000	6	675
-	102	5 700 to 190 000	47 500	7	750
2600	-	5 700 to 191 000	48 000	7	775
-	108	6 500 to 210 000	55 000	7	850
2800	-	6 700 to 222 000	55 500	8	875
-	114	7 100 to 237 000	59 500	8	950
3000	-	7 600 to 254 000	63 500	9	1025
-	120	7 900 to 263 000	65 500	9	1050

Flow characteristic values in US units: 1 to 48" (DN 25 to 1200)

Nominal diameter		Recommended flow rate min./max. full scale value (v ~ 0.3/10 m/s)	Full scale value current output (v ~ 2.5 m/s)	Factory settings	
[in]	[mm]			[gal/min]	Pulse value (~ 2 pulse/s) [gal]
1	25	2.5 to 80	18	0.2	0.25
-	32	4 to 130	30	0.2	0.5
1 ½	40	7 to 185	50	0.5	0.75
2	50	10 to 300	75	0.5	1.25
-	65	16 to 500	130	1	2

Nominal diameter		Recommended flow rate min./max. full scale value (v ~ 0.3/10 m/s)	Full scale value current output (v ~ 2.5 m/s)	Factory settings	
[in]	[mm]			[gal/min]	Pulse value (~ 2 pulse/s) [gal]
3	80	24 to 800	200	2	2.5
4	100	40 to 1250	300	2	4
–	125	60 to 1950	450	5	7
6	150	90 to 2650	600	5	12
8	200	155 to 4850	1200	10	15
10	250	250 to 7500	1500	15	30
12	300	350 to 10600	2400	25	45
14	350	500 to 15000	3600	30	60
15	375	600 to 19000	4800	50	60
16	400	600 to 19000	4800	50	60
18	450	800 to 24000	6000	50	90
20	500	1000 to 30000	7500	75	120
24	600	1400 to 44000	10500	100	180
28	700	1900 to 60000	13500	125	210
30	750	2150 to 67000	16500	150	270
32	800	2450 to 80000	19500	200	300
36	900	3100 to 100000	24000	225	360
40	1000	3800 to 125000	30000	250	480
42	–	4200 to 135000	33000	250	600
48	1200	5500 to 175000	42000	400	600

Flow characteristic values in US units: 54 to 120" (DN 1400 to 3000)

Nominal diameter		Recommended flow rate min./max. full scale value (v ~ 0.3/10 m/s)	Full scale value current output (v ~ 2.5 m/s)	Factory settings	
[in]	[mm]			[Mgal/d]	Pulse value (~ 2 pulse/s) [Mgal]
54	–	9 to 300	75	0.0005	1.3
–	1400	10 to 340	85	0.0005	1.3
60	–	12 to 380	95	0.0005	1.3
–	1600	13 to 450	110	0.0008	1.7
66	–	14 to 500	120	0.0008	2.2
72	1800	16 to 570	140	0.0008	2.6
78	–	18 to 650	175	0.0010	3.0
–	2000	20 to 700	175	0.0010	2.9
84	–	24 to 800	190	0.0011	3.2
–	2200	26 to 870	210	0.0012	3.4
90	–	27 to 910	220	0.0013	3.6
–	2400	31 to 1030	245	0.0014	4.1

Nominal diameter		Recommended flow rate min./max. full scale value (v ~ 0.3/10 m/s)	Full scale value current output (v ~ 2.5 m/s)	Factory settings	
[in]	[mm]			Pulse value (~ 2 pulse/s)	Low flow cut off (v ~ 0.04 m/s)
		[Mgal/d]	[Mgal/d]	[Mgal]	[Mgal/d]
96	-	32 to 1066	265	0.0015	4.0
102	-	34 to 1203	300	0.0017	5.0
-	2600	34 to 1212	305	0.0018	5.0
108	-	35 to 1300	340	0.0020	5.0
-	2800	42 to 1405	350	0.0020	6.0
114	-	45 to 1503	375	0.0022	6.0
-	3000	48 to 1613	405	0.0023	6.0
120	-	50 to 1665	415	0.0024	7.0

Output

Output versions	20
Output signal	20
Signal on alarm	23
Low flow cut off	23
Galvanic isolation	23
Protocol-specific data	24

Output versions

Order code 020: output; input	Output version
Option B	<ul style="list-style-type: none"> ▪ Current output 4 to 20 mA HART ▪ Pulse/frequency/switch output
Option F	IO-Link
Option M	<ul style="list-style-type: none"> ▪ Modbus RS485 ▪ Current output 4 to 20 mA

Output signal

Current output 4 to 20 mA HART / 4 to 20 mA HART Ex-i

Signal mode	Choose via terminal assignment: <ul style="list-style-type: none"> ▪ Active ▪ Passive
Current range	Can be set to: <ul style="list-style-type: none"> ▪ 4 to 20 mA NAMUR ▪ 4 to 20 mA US ▪ 4 to 20 mA ▪ Fixed current
Max. output current	21.5 mA
Open-circuit voltage	DC < 28.8 V (active)
Max. input voltage	DC 30 V (passive)
Max. load	400 Ω
Resolution	1 μA
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	<ul style="list-style-type: none"> ▪ Off ▪ Volume flow ▪ Mass flow ▪ Conductivity* ▪ Noise* ▪ Coil current shot time* <p>* Visibility depends on order options or device settings</p>

IO-Link

Physical interface	Similar to the standard IEC 61131-9
Signal	Digital communication signal IO-Link, 3-wire
IO-Link version	1.1
IO-Link SSP version	Smart Sensor Profile 2nd Edition V1.2
IO-Link device port	IO-Link port class A

Modbus RS485

Physical interface	RS485 in accordance with EIA/TIA-485 standard
--------------------	---

Current output 4 to 20 mA ¹⁾

Signal mode	Choose via terminal assignment: <ul style="list-style-type: none"> ▪ Active ▪ Passive
Current range	Can be set to: <ul style="list-style-type: none"> ▪ 4 to 20 mA NAMUR ▪ 4 to 20 mA US ▪ 4 to 20 mA ▪ Fixed current
Max. output current	21.5 mA
Open-circuit voltage	DC < 28.8 V (active)
Max. input voltage	DC 30 V (passive)
Max. load	400 Ω
Resolution	1 μA
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	<ul style="list-style-type: none"> ▪ Off ▪ Volume flow ▪ Mass flow ▪ Conductivity* ▪ Noise* ▪ Coil current shot time* <p>* Visibility depends on order options or device settings</p>

Pulse/frequency/switch output ²⁾

Function	Can be set to: <ul style="list-style-type: none"> ▪ Pulse output ▪ Frequency output ▪ Switching output
Version	Open collector: Passive
Input values	<ul style="list-style-type: none"> ▪ DC 10.4 to 30 V ▪ Max. 140 mA
Voltage drop	<ul style="list-style-type: none"> ▪ ≤ DC 2 V @ 100 mA ▪ ≤ DC 2.5 V @ max. input current

Pulse output	
Pulse width	Configurable: 0.05 to 2 000 ms
Max. pulse rate	10 000 Impulse/s
Pulse value	Configurable
Assignable measured variables	<ul style="list-style-type: none"> ▪ Volume flow ▪ Mass flow

Frequency output	
Output frequency	Configurable: end value frequency 2 to 10 000 Hz ($f_{max} = 12\,500$ Hz)
Damping	Configurable: 0 to 999.9 s

1) Only available with Modbus RS485
 2) Only available with 4 to 20 mA HART

Pulse/pause ratio	1:1
Assignable measured variables	<ul style="list-style-type: none"> ■ Off ■ Volume flow ■ Mass flow ■ Conductivity* ■ Noise* ■ Coil current shot time* ■ Reference electrode potential against PE* <p>* Visibility depends on order options or device settings</p>
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Configurable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	<ul style="list-style-type: none"> ■ Off ■ On ■ Diagnostic behavior: <ul style="list-style-type: none"> ■ Alarm ■ Warning ■ Warning and alarm ■ Limit value: <ul style="list-style-type: none"> ■ Off ■ Volume flow ■ Mass flow ■ Flow velocity ■ Conductivity* ■ Corrected conductivity* ■ Totalizer 1...3 ■ Flow direction monitoring ■ Status <ul style="list-style-type: none"> ■ Empty pipe detection ■ Low flow cut off <p>* Visibility depends on order options or device settings</p>

Signal on alarm

Output behavior in the event of a device alarm (failure mode)

HART

Device diagnostics	Device condition can be read out via HART Command 48
---------------------------	--

IO-Link

Operating mode	Digital transmission of all failure information
Device status	Readable via cyclic and acyclic data transmission

Modbus RS485

Failure mode	Selectable: <ul style="list-style-type: none"> ▪ NaN value instead of current value ▪ Last valid value
---------------------	--

Current output 4 to 20 mA

4 to 20 mA	Selectable: <ul style="list-style-type: none"> ▪ Min. value: 3.59 mA ▪ Max. value: 21.5 mA ▪ Freely definable value between: 3.59 to 21.5 mA ▪ Actual value ▪ Last valid value
-------------------	---

Pulse/frequency/switch output

Pulse output	Selectable: <ul style="list-style-type: none"> ▪ Actual value ▪ No pulses
Frequency output	Selectable: <ul style="list-style-type: none"> ▪ Actual value ▪ 0 Hz ▪ Defined value: 0 to 12 500 Hz
Switch output	Selectable: <ul style="list-style-type: none"> ▪ Current status ▪ Open ▪ Closed

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

The outputs are galvanically isolated from one another and from earth.

Protocol-specific data

HART

Bus structure	The HART signal is superimposed on the 4 to 20 mA current output.
Manufacturer ID	0x11
Device type ID	0x71
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	At least 250 Ω
System integration	Measured variables via HART protocol

IO-Link

IO-Link specification	Version 1.1.3
Device ID	9728257
Manufacturer ID	17
Smart Sensor Profile	Smart Sensor Profile 2nd Edition V1.2; supported <ul style="list-style-type: none"> ▪ Identification and Diagnosis ▪ Digital Measuring and Switching Sensor (as per SSP type 4.3.4) ▪ Function Class Sensor Control Wide
Smart Sensor Profile Type	Measuring profile type 4.3.4 Measuring and Switching Sensor, floating point, 4 channel
SIO mode	No
Speed	COM2 (38.4 kBaud)
Minimum cycle time	12 ms
Process data width	Input: 18 bytes (as per SSP 4.3.4) Output: 2 bytes (as per SSP 4.3.4)
OnRequestdata	8 bytes
Data storage	Yes
Block configuration	Yes
Device operational	The device is operational 6 s after the supply voltage has been applied
System integration	Cyclic input measured variables: <ul style="list-style-type: none"> ▪ Volume flow [m³/h] ▪ Conductivity [S/m], depending on order options or device settings ▪ Temperature [°C], depending on the sensor option selected ▪ Totalizer 1 [m³] Cyclic output measured variables: <ul style="list-style-type: none"> ▪ Totalizer submenu – Totalize option ▪ Totalizer submenu – Reset + hold option ▪ Totalizer submenu – Reset + totalize option ▪ Totalizer submenu – Hold option ▪ Flow override ▪ Device search

Device description


In order to integrate field devices into a digital communication system, the IO-Link system needs a description of the device parameters, such as output data, input data, data format, data volume and supported transmission rate.

These data are available in the device description (IODD) which is provided to the IO-Link Master when the communication system is commissioned.

The IODD can be downloaded as follows:

- www.endress.com
- <https://ioddfinder.io-link.com>

Modbus RS485

Physical interface	RS485 in accordance with EIA/TIA-485 standard
Terminating resistor	Not integrated
Protocol	Modbus Applications Protocol Specification V1.1
Response times	<ul style="list-style-type: none"> ▪ Direct data access: typically 25 to 50 ms ▪ Auto-scan buffer (data range): typically 3 to 5 ms
Device type	Slave
Slave address range	1 to 247
Broadcast address range	0
Function codes	<ul style="list-style-type: none"> ▪ 03: Read holding register ▪ 04: Read input register ▪ 06: Write single registers ▪ 08: Diagnostics ▪ 16: Write multiple registers ▪ 23: Read/write multiple registers
Broadcast messages	<p>Supported by the following function codes:</p> <ul style="list-style-type: none"> ▪ 06: Write single registers ▪ 16: Write multiple registers ▪ 23: Read/write multiple registers
Supported baud rate	<ul style="list-style-type: none"> ▪ 1 200 BAUD ▪ 2 400 BAUD ▪ 4 800 BAUD ▪ 9 600 BAUD ▪ 19 200 BAUD ▪ 38 400 BAUD ▪ 57 600 BAUD ▪ 115 200 BAUD
Data transfer mode	RTU
Data access	<p>Each parameter can be accessed via Modbus RS485.</p> <p> For Modbus register information</p>
System integration	<p>Information on system integration .</p> <ul style="list-style-type: none"> ▪ Modbus RS485 information ▪ Function codes ▪ Register information ▪ Response time ▪ Modbus data map

Power supply

Terminal assignment	28
Supply voltage	28
Power consumption	29
Current consumption	29
Power supply failure	29
Electrical connection	29
Potential equalization	33
Terminals	35
Cable entries	35
Overvoltage protection	36

Terminal assignment



The terminal assignment is documented on an adhesive label.

The following terminal assignment is available:

Current output 4 to 20 mA HART (active) and pulse/frequency/switch output

Supply voltage		Output 1				Output 2	
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)
L/+	N/-	Current output 4 to 20 mA HART (active)		-		Pulse/frequency/switch output (passive)	

Current output 4 to 20 mA HART (passive) and pulse/frequency/switch output

Supply voltage		Output 1				Output 2	
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)
L/+	N/-	-		Current output 4 to 20 mA HART (passive)		Pulse/frequency/switch output (passive)	

Modbus RS485 and current output 4 to 20 mA (active)

Supply voltage		Output 1				Output 2	
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (B)	23 (A)
L/+	N/-	Current output 4 to 20 mA (active)		-		Modbus RS485	

Modbus RS485 and current output 4 to 20 mA (passive)

Supply voltage		Output 1				Output 2	
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (B)	23 (A)
L/+	N/-	-		Current output 4 to 20 mA (passive)		Modbus RS485	

Supply voltage

Order code for "Power supply"	Terminal voltage	Frequency range
Option A IO-Link port class A	DC 18 to 30 V ¹⁾	-
Option D	DC 24 V	-20 to +30 %
Option E	AC 100 to 240 V	-15 to +10 %
Option I	DC 24 V	-20 to +30 %
	AC 100 to 240 V	-15 to +10 %
Option M non-hazardous area	DC 24 V	-20 to +30 %
	AC 100 to 240 V	-15 to +10 %

1) These values are absolute minimum and maximum values. No tolerance applies. The DC power unit must be tested to ensure it meets technical safety requirements (e.g. PELV, SELV) with limited power sources (e.g. Class 2).

Power consumption

- Transmitter:
 - HART, Modbus RS485: Max. 10 W (active power)
 - IO-Link: Max. 6 W (active power)
- Switch-on current:
 - HART, Modbus RS485: Max. 36 A (< 5 ms) as per NAMUR Recommendation NE 2.1
 - IO-Link: Max. 400 mA

Current consumption


- Max. 400 mA (24 V)
- Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)
- Max 200 mA. (18 to 30 V, IO-Link port class A)

Power supply failure

- Totalizers stop at the last value measured.
- Device configuration remains unchanged.
- Error messages (incl. total operated hours) are stored.



Electrical connection


Connections and terminal assignment, remote version connecting cable



- 1 Outer ground terminal
- 2 Transmitter housing: cable entry for coil current cable
- 3 Coil current cable
- 4 Transmitter housing: cable entry for electrode cable
- 5 Electrode cable
- 6 Sensor connection housing: cable entry for electrode cable
- 7 Outer ground terminal
- 8 Sensor connection housing: cable entry for coil current cable


Transmitter terminal connections

 Terminal assignment → [Terminal assignment](#),  28




A0043283

- 1 Cable entry for power supply cable: supply voltage
- 2 Outer ground terminal: on transmitters made of polycarbonate with a metal pipe adapter
- 3 Cable entry for signal cable
- 4 Outer ground terminal



A0045438


- 1 Cable entry for power supply cable: supply voltage
- 2 Cable entry for signal cable
- 3 Outer ground terminal



A0053767

- 1 M12 plug for power supply (supply voltage) and signals (IO-Link)
- 2 Dummy plug
- 3 Outer ground terminal

Pin assignment of IO-Link device plug




A0053891

- 1 M12 A-coded (IEC 61076-2-101)
- 1 PIN 1: power supply
- 2 PIN 2: not used
- 3 PIN 3: reference potential for power supply/output
- 4 PIN 4: output 1 (IO-link)

Examples of electric terminals


Current output 4 to 20 mA HART



A0055862

2 Connection example for 4 to 20 mA current output with HART (active)

- 1 Automation system with 4 to 20 mA current input with HART (e.g. PLC)
- 2 Optional display unit: Note maximum load
- 3 Transmitter with 4 to 20 mA current output with HART (active)
- 4 Ground the cable shield on one side only. For installations in compliance with NAMUR NE98, grounding of the cable shield on both sides is required.



A0055861


3 Connection example for 4 to 20 mA current output with HART (passive)

- 1 Automation system with 4 to 20 mA current input with HART (e.g. PLC)
- 2 Power supply
- 3 Optional display unit: Note maximum load
- 4 Transmitter with 4 to 20 mA current output with HART (passive)
- 5 Ground the cable shield on one side only. For installations in compliance with NAMUR NE98, grounding of the cable shield on both sides is required.

IO-Link

See <https://io-link.com>"IO-Link System Description"

Modbus RS485




A0055863

4 Connection example for Modbus RS485

- 1 Automation system with Modbus master (e.g. PLC)
- 2 Optional distribution box
- 3 Transmitter with Modbus RS485


Current output 4 to 20 mA (without HART)



A0055851

5 Connection example for 4 to 20 mA current output (active)

- 1 Automation system with current input (e.g. PLC)
- 2 Optional additional display unit: Observe maximum load
- 3 Flowmeter with current output (active)




A0055852

6 Connection example for 4 to 20 mA current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Optional additional display unit: Observe maximum load
- 4 Transmitter with current output (passive)

Pulse output/frequency output/switch output



7 Connection example for pulse output/frequency output/switch output (passive)

- 1 Automation system with pulse input/frequency input/switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter with pulse output/frequency output/switch output (passive)

Potential equalization

Introduction

Correct potential equalization (equipotential bonding) is a prerequisite for stable and reliable flow measurement. Inadequate or incorrect potential equalization can result in device failure and present a safety hazard.

The following requirements must be observed to ensure correct, trouble-free measurement:


- The principle that the medium, the sensor and the transmitter must be at the same electric potential applies.
- Take in-company grounding guidelines, materials and the grounding conditions and potential conditions of the pipe into consideration.
- The necessary potential equalization connections must be established using a ground cable with a minimum cross-section of 6 mm² (0.0093 in²). Also use a cable lug.
- In the case of remote device versions, the ground terminal in the example always refers to the sensor and not to the transmitter.

i Accessories such as ground cables and ground disks can be ordered from Endress +Hauser → *Device-specific accessories*, 134

Abbreviations used

- PE (Protective Earth): potential at the potential equalization terminals of the device
- P_P (Potential Pipe): potential of the pipe, measured at the flanges
- P_M (Potential Medium): potential of the medium

Connection examples for standard situations




Unlined and grounded metal pipe

- Potential equalization is via the measuring tube.
- The medium is set to ground potential.

Starting conditions:

- Pipes are correctly grounded on both sides.
- Pipes are conductive and at the same electric potential as the medium
- ▶ Connect the connection housing of the transmitter or sensor to ground potential via the ground terminal provided for this purpose.




Unlined metal pipe

- Potential equalization is via the ground terminal and pipe flanges.
- The medium is set to ground potential.

Starting conditions:

- Pipes are not sufficiently grounded.
- Pipes are conductive and at the same electric potential as the medium

1. Connect both sensor flanges to the pipe flange via a ground cable and ground them.
2. Connect the connection housing of the transmitter or sensor to ground potential via the ground terminal provided for this purpose.
3. For $DN \leq 300$ (12"): Mount the ground cable directly on the conductive flange coating of the sensor with the flange screws.
4. For $DN \geq 350$ (14"): Mount the ground cable directly on the metal transport bracket. Observe the screw tightening torques: see the Brief Operating Instructions for the sensor.



Plastic pipe or pipe with insulating liner

- Potential equalization is via the ground terminal and ground disks.
- The medium is set to ground potential.


Starting conditions:

- The pipe has an insulating effect.
- Low-impedance medium grounding close to the sensor is not guaranteed.
- Equalizing currents through the medium cannot be ruled out.

1. Connect the ground disks via the ground cable to the ground terminal of the connection housing of the transmitter or sensor.
2. Connect the connection to ground potential.

Connection example with the potential of medium not equal to potential equalization connection without the "Floating measurement" option

In these cases, the medium potential can differ from the potential of the device.



Metal, ungrounded pipe

The sensor and transmitter are installed in a way that provides electrical insulation from PE, e.g. applications for electrolytic processes or systems with cathodic protection.

Starting conditions:

- Unlined metal pipe
- Pipes with an electrically conductive liner

1. Connect the pipe flanges and transmitter via the ground cable.
2. Route the shielding of the signal lines via a capacitor (recommended value $1.5\mu\text{F}/50\text{V}$).
3. Device connected to power supply such that it is floating in relation to the potential equalization connection (isolation transformer). This measure is not required in the case of 24V DC supply voltage without PE (= SELV power unit).

Connection examples with the potential of medium not equal to potential equalization connection with the "Floating measurement" option

In these cases, the medium potential can differ from the potential of the device.

Introduction

The "Floating measurement" option enables the galvanic isolation of the measuring system from the device potential. This minimizes harmful equalizing currents caused by


differences in potential between the medium and the device. The "Floating measurement" option is optionally available: order code for "Sensor option", option CV

Operating conditions for use of the "Floating measurement" option

Device version	Compact version and remote version (length of connecting cable ≤ 10 m)
Differences in voltage between medium potential and device potential	As small as possible, usually in the mV range
Alternating voltage frequencies in the medium or at ground potential (PE)	Below typical power line frequency in the country

i To achieve the specified conductivity measuring accuracy, a conductivity calibration is recommended when the device is installed.

A full pipe adjustment is recommended when the device is installed.




Plastic pipe

Sensor and transmitter are correctly grounded. A difference in potential can occur between the medium and potential equalization connection. Potential equalization between P_M and PE via the reference electrode is minimized with the "Floating measurement" option.

Starting conditions:

- The pipe has an insulating effect.
- Equalizing currents through the medium cannot be ruled out.

1. Use the "Floating measurement" option, while also observing the operating conditions for floating measurement.
2. Connect the connection housing of the transmitter or sensor to ground potential via the ground terminal provided for this purpose.



Metal, ungrounded pipe with insulating liner

The sensor and transmitter are installed in a way that provides electrical insulation from PE. The medium and pipe have different potentials. The "Floating measurement" option minimizes harmful equalizing currents between P_M and P_p via the reference electrode.

Starting conditions:

- Metal pipe with insulating liner
- Equalizing currents through the medium cannot be ruled out.

1. Connect the pipe flanges and transmitter via the ground cable.
2. Route the shielding of the signal cables via a capacitor (recommended value 1.5µF/ 50V).
3. Device connected to power supply such that it is floating in relation to the potential equalization connection (isolation transformer). This measure is not required in the case of 24V DC supply voltage without PE (= SELV power unit).
4. Use the "Floating measurement" option, while also observing the operating conditions for floating measurement.

Terminals

Spring terminals

- Suitable for strands and strands with ferrules.
- Conductor cross-section 0.2 to 2.5 mm² (24 to 12 AWG).

Cable entries

- Cable gland: M20 × 1.5 for cable Ø6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
 - NPT ½"
 - G ½", G ½" Ex d
 - M20
- M12 plug-in connector (IO-Link only)

Overvoltage protection

Mains voltage fluctuations	→ <i>Supply voltage</i> , 28
Overvoltage category	Overvoltage category II
Short-term, temporary overvoltage	Between cable and neutral conductor up to 1200 V for max. 5s
Long-term, temporary overvoltage	Up to 500 V between cable and ground

Cable specifications

Requirements for connecting cable	38
Ground cable requirements	38
Connecting cable requirements	38

Requirements for connecting cable

Electrical safety

As per applicable national regulations.

Permitted temperature range

- Observe the installation guidelines that apply in the country of installation.
- The cables must be suitable for the minimum temperatures and maximum temperatures to be expected.

Power supply cable (incl. conductor for the inner ground terminal)

- A standard installation cable is sufficient.
- Provide grounding according to applicable national codes and regulations.

Signal cable

- Current output 4 to 20 mA HART:
A shielded cable is recommended, observe the grounding concept of the facility.
- Pulse/frequency/switch output:
Standard installation cable
- IO-Link:
Twisted three- or four-core cable M12 A-coded according to IEC 61076-2-101 recommended with
 - Conductor cross-section: 0.34 mm² (AWG22)
 - Max. cable length: 20 m
- Modbus RS485:
Cable type A according to EIA/TIA-485 standard is recommended
- Current output 4 to 20 mA:
Standard installation cable

Ground cable requirements

Copper wire: at least 6 mm² (0.0093 in²)

Connecting cable requirements



Connecting cable only necessary for remote version.

Electrode cable	Coil current cable
<p style="text-align: right; font-size: small;">A0054679</p> <p>1 GND (green): Ground-wire 0.38 mm² (AWG 21)</p> <p>2 E1 (brown): "Electrode E1" - core 0.38 mm² (AWG 21)</p> <p>3 E (yellow): grounding 0.38 mm² (AWG 21)</p> <p>4 E2 (white): "Electrode E2" - core 0.38 mm² (AWG 21)</p> <p>a Outer jacket</p> <p>b Cable shield</p> <p>c Core jacket</p> <p>d Core shield</p> <p>e Core insulation</p> <p>f Core</p>	<p style="text-align: right; font-size: small;">A0054680</p> <p>1 ER+ (black): coil current core 0.75 mm² (AWG 18)</p> <p>2 ER- (black): coil current core 0.75 mm² (AWG 18)</p> <p>3 NC (yellow-green): not connected 0.75 mm² (AWG 18)</p> <p>a Outer jacket</p> <p>b Cable shield</p> <p>c Core insulation</p> <p>d Core</p> <p>e Core reinforcement</p>

i **Preterminated connecting cables**

Two connecting cable versions can be ordered from Endress+Hauser for use with IP68 protection:

- Cable is already connected to the sensor.
- Cable is connected by the customer (incl. tools for sealing the connection compartment).

i **Armored connecting cable**

Armored connecting cables with additional, metal reinforcing braid can be ordered from Endress+Hauser. Armored connecting cables are used:

- When laying the cable directly in the ground
- Where there is a risk of damage from rodents
- If using the device below IP68 degree of protection

Electrode cable

Design	3×0.38 mm ² (21 AWG) with common, braided copper shield (∅ ~ 9.5 mm (0.37 in)) and individual shielded cores If using the empty pipe detection (EPD) function: 4×0.38 mm ² (21 AWG) with common, braided copper shield (∅ ~ 9.5 mm (0.37 in)) and individual shielded cores
Conductor resistance	≤ 50 Ω/km (0.015 Ω/ft)
Capacitance: core/shield	≤ 420 pF/m (128 pF/ft)
Cable length	Depends on the medium conductivity: maximum 200 m (656 ft)
Cable lengths (available for order)	5 m (15 ft), 10 m (30 ft), 20 m (60 ft) or variable length: maximum 200 m (656 ft) Armored cables: variable length up to maximum 200 m (656 ft)
Operating temperature	-20 to +80 °C (-4 to +176 °F)

Coil current cable

Design	3×0.75 mm ² (18 AWG) with common, braided copper shield (∅ ~ 9.5 mm (0.37 in)) and individual shielded cores
Conductor resistance	≤ 37 Ω/km (0.011 Ω/ft)
Capacitance: core/shield	≤ 120 pF/m (37 pF/ft)

Cable length	Depends on the medium conductivity, max. 200 m (656 ft)
Cable lengths (available for order)	5 m (15 ft), 10 m (30 ft), 20 m (60 ft) or variable length up to max. 200 m (656 ft) Armored cables: variable length up to max. 200 m (656 ft)
Operating temperature	-20 to +80 °C (-4 to +176 °F)
Test voltage for cable insulation	≤ AC 1 433 V rms 50/60 Hz or ≥ DC 2 026 V

Performance characteristics

Reference operating conditions	42
Maximum measurement error	42
Repeatability	43
Influence of ambient temperature	43

Reference operating conditions

- Error limits based on ISO 20456:2017
- Water, typically: +15 to +45 °C (+59 to +113 °F); 0.5 to 7 bar (73 to 101 psi)
- Data as indicated in the calibration protocol
- Accuracy based on accredited calibration rigs according to ISO 17025

i To obtain measured errors, use the *Applicator* sizing tool → *Service-specific accessory*, 136

Maximum measurement error


o. r. = of reading

Maximum permissible error under reference operating conditions

Volume flow

±0.5 % o. r. ±1 mm/s (±0.04 in/s)

i Fluctuations in the supply voltage have no effect within the specified range.



8 Maximum measurement error in % o.r.


Electrical conductivity

Order code for "Conductivity measurement", option CX

The values apply for:

- Measurements at a reference temperature of +25 °C (+77 °F).
If the temperature differs, the temperature coefficient of the medium must be taken into account (typically 2.1%/K).
- Device version: compact (transmitter and sensor form a mechanical unit)
- Devices in a metal pipe or in a non-metal pipe with installed ground disks.
- Devices whose potential equalization has been established according to the specifications in the related Operating Instructions.

Conductivity [$\mu\text{S}/\text{cm}$]	Measurement error [%] o. r.
5 to 20	± 20%
20 to 20000	± 10%
20000 to 100000	± 20%



9 Measurement error for order code "Conductivity measurement", option CX

Accuracy of outputs

Current output	±5 µA
Pulse/frequency output	Max. ±100 ppm o. r. (across the entire ambient temperature range)

Repeatability

Volume flow	Max. ±0.1 % o. r. ± 0.5 mm/s (0.02 in/s)
Electrical conductivity	Max. ±5 % o. r. (5 to 100 000 µS/cm)

Influence of ambient temperature

Current output	Temperature coefficient max. 1 µA/°C
Pulse/frequency output	No additional effect. Is included in the accuracy.




Installation

Installation conditions

Installation conditions

Flow direction




Install the device in the direction of flow.



Note the direction of arrow on the nameplate.

Installation with inlet runs and outlet runs


Installation requires inlet and outlet runs: devices with the order code for "Design", option D, E, F and G.



Ensure straight, undisturbed inlet and outlet runs.



To avoid negative pressure and to comply with accuracy specifications, install the sensor upstream from assemblies that produce turbulence (e.g. valves, T-sections) and downstream from pumps → *Installation near pumps*, 49.



Keep a sufficient distance to the next pipe elbow.

Installation without inlet runs and outlet runs

Depending on the device design and installation location, the inlet and outlet runs can be reduced or omitted entirely.




Maximum measurement error

When the device is installed with the inlet and outlet runs described, a maximum measurement error of $\pm 0.5\%$ of the reading ± 1 mm/s (0.04 in/s) can be guaranteed.

Devices and possible order options


Order code for "Design"		
Option	Description	Design
H	Lap joint flange, 0 x DN inlet/outlet runs	0 x DN full-bore design ¹⁾
I	Fixed flange, 0 x DN inlet/outlet runs	
J	Fixed flange, short installed length, 0 x DN inlet/outlet runs	
K	Fixed flange, long installed length, 0 x DN inlet/outlet runs	

1) "Full-bore" indicates a measuring tube cross-section corresponding to the nominal diameter without constriction. This means there is no pressure loss.



Installation before or after bends
Installation without inlet and outlet runs is possible.


A0032859



Installation downstream of pumps
Installation without inlet and outlet runs is possible.

i An inlet run of $\geq 2 \times DN$ is recommended.


A0045530



Installation upstream of valves
Installation without inlet and outlet runs is possible.

i An outlet run of $\geq 1 \times DN$ is recommended.

A0045531




Installation downstream of valves
The device can be installed without inlet and outlet runs if the valve is 100% open during operation.

i An inlet run of $\geq 2 \times DN$ is recommended if the valve is 100% open during operation.


A0045786

Orientations



Vertical orientation, upward direction of flow
For all applications.

A0041159




Horizontal orientation, transmitter at top

This orientation is suitable for the following applications:

- For medium and low process temperatures, in order to maintain the minimum ambient temperature for the transmitter.
- For empty pipe detection, even in the case of empty or partially filled measuring pipes.

A0041160




Horizontal orientation, transmitter at bottom

This orientation is suitable for the following applications:

- For medium and high process temperatures, in order to maintain the maximum ambient temperature for the transmitter.
- To prevent the electronics module from overheating in the case of a sharp rise in temperature (e.g. CIP or SIP processes), install the measuring instrument with the transmitter component pointing downwards.

A0041161

This orientation is not suitable for the following applications:
If empty pipe detection is to be used.




Horizontal orientation, transmitter at side

This orientation is not suitable

A0041162

Vertical


Optimum for self-emptying pipe systems and for use in conjunction with empty pipe detection.



A0015591

Horizontal

- Ideally, the measuring electrode plane should be horizontal. This prevents brief insulation of the measuring electrodes by entrained air bubbles.
- Empty pipe detection only works if the transmitter housing is pointing upwards as otherwise there is no guarantee that the empty pipe detection function will actually respond to a partially filled or empty measuring tube.




A0029344

- 1 EPD electrode for empty pipe detection
- 2 Measuring electrodes for signal detection
- 3 Reference electrode for potential equalization


Mounting locations

- Do not install the device at the highest point of the pipe.
- Do not install the device upstream from a free pipe outlet in a down pipe.




A0042131

The device should ideally be installed in an ascending pipe.




A0042317

Installation near control valves



Install the device in the direction of flow upstream from the control valve.

Installation upstream from a down pipe




NOTICE

Negative pressure in the measuring pipe can damage the liner!

- ▶ If installing upstream from down pipes with a length $h \geq 5$ m (16.4 ft): install a siphon with a vent valve downstream from the device.

i This arrangement prevents the flow of liquid stopping in the pipe and air entrainment.


Installation with partially filled pipes



- Partially filled pipes with a gradient require a drain-type configuration.
- The installation of a cleaning valve is recommended.

i For devices with the order code for "Design", option H, I, J or K no inlet or outlet runs need to be considered.

Installation near pumps



NOTICE


A vacuum in the measuring tube can damage the liner!

- ▶ Install the device in the direction of flow downstream from the pump.
- ▶ Install pulsation dampers if reciprocating, diaphragm or peristaltic pumps are used.

i

- Information on the liner's resistance to partial vacuum → *Pressure tightness*, 63
- Information on the measuring system's resistance to vibration and shock → *Vibration resistance and shock resistance*, 55

Installation of heavy devices



Support is required with nominal diameters of $DN \geq 350$ (14") and higher.

NOTICE

Damage to the device!

If incorrect support is provided, the sensor housing could buckle and the internal magnetic coils could be damaged.

- ▶ Only provide supports at the pipe flanges.


Pipe vibrations

A remote version is recommended in the event of strong pipe vibrations.

NOTICE

Pipe vibrations can damage the device!

- ▶ Do not expose the device to strong vibrations.
- ▶ Support the pipe and fix it in place.
- ▶ Support the device and fix it in place.
- ▶ Mount the sensor and transmitter separately.




A0041092

Adapters

Suitable adapters (double-flange reducers) can be used to install the sensor in larger-diameter pipes. The resulting higher rate of flow improves measuring accuracy with very slow-moving media.

i The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders. It only applies to liquids with a viscosity similar to that of water.

1. Calculate the ratio of the diameters d/D .
2. Determine the flow velocity after the reduction.
3. From the chart, determine the pressure loss as a function of the flow velocity v and the d/D ratio.



A0041086


Seals

Note the following when installing seals:

- For liner with polyurethane: no seal is required.
- For "PTFE" liner: no seal is required.
- For liner with hard rubber: seal is **always** required.
- For DIN flanges: only install seals according to DIN EN 1514-1.

Thermal insulation

The sensor and pipe must be insulated in the event of very hot media. The insulation helps to slow energy loss and prevent injuries from accidental contact with hot pipes.



A0041093


NOTICE

If the meter electronics overheat this can damage the device!

- ▶ Keep the housing support completely free (heat dissipation).
- ▶ Provide insulation but make sure it does not go beyond the upper edge of the two sensor half-shells.


Magnetism and static electricity

Do not install the device near magnetic fields, e.g. Engines, transformers.



A0042152

Outdoor use



A0023989

- Avoid exposure to direct sunlight.
- Install in a location protected from sunlight.
- Avoid direct exposure to weather conditions.
- Use a weather protection cover → *Transmitter*, 134.

Immersion in water

i Only the remote version with IP68, type 6P, is suitable for immersion in water.

NOTICE

If the maximum water depth and operating duration are exceeded, this will damage the device!

- ▶ Observe the maximum water depth and operating duration.

Order code for "Sensor option", options CB, CC

Use of device under water at a maximum water depth of:


- 3 m (10 ft): permanent use
- 10 m (30 ft): max. 48 hours

Order code for "Sensor option", option CQ "IP68, Type 6P, factory-potted"

- For permanent operation of the device under rain or surface water
- Operation at a maximum depth of 3 m (10 ft)

Order code for "Sensor option", options CD, CE

- For the operation of the device under water and in saline water
- Operating duration at a maximum depth of:
 - 3 m (10 ft): permanent use
 - 10 m (30 ft): maximum 48 hours



A0042412


Use in buried applications

i Only the remote version with IP68 is suitable for use in buried applications.

Order code for "Sensor option", options CD, CE

The device can be used in buried applications without the need to implement additional precautionary measures on the device.

Installation is performed according to regional installation regulations.




A0042646

Environment

Ambient temperature range	54
Storage temperature	54
Relative humidity	54
Operating height	54
Atmosphere	54
Degree of protection	54
Vibration resistance and shock resistance	55
Electromagnetic compatibility (EMC)	55

Ambient temperature range

Transmitter	-40 to +60 °C (-40 to +140 °F)
Local display	-20 to +60 °C (-4 to +140 °F) The readability of the display may be impaired at temperatures outside the temperature range.
Sensor	<ul style="list-style-type: none"> ▪ Process connection, carbon steel: -10 to +60 °C (+14 to +140 °F) ▪ Process connection, stainless steel: -40 to +60 °C (-40 to +140 °F)
Liner	Do not exceed or fall below the permitted temperature range of the liner → <i>Medium temperature range</i> , 58.  Dependency of ambient temperature on medium temperature → <i>Medium temperature range</i> , 58

Storage temperature

The storage temperature corresponds to the ambient temperature range of the transmitter and sensor.

Relative humidity

The device is suitable for use in outdoor and indoor areas with a relative humidity of 5 to 95%.

Operating height

According to EN 61010-1

- Without overvoltage protection: ≤ 2 000 m
- With overvoltage protection: > 2 000 m (e.g. Endress+Hauser HAW series)

Atmosphere

According to IEC 60529: If a plastic housing is permanently exposed to certain steam and air mixtures, this can damage the housing.

 More Informationen: Endress+Hauser sales organizations.

Degree of protection

Transmitter	<ul style="list-style-type: none"> ▪ IP66/67, Type 4X enclosure, suitable for pollution degree 4 ▪ Open housing: IP20, Type 1 enclosure, suitable for pollution degree 2 	
Sensor	IP66/67, Type 4X enclosure, suitable for pollution degree 4	
Optional sensor		
Order code for "Sensor option", Option CB, CC	IP68, Type 6P enclosure Fully welded, with protective coating as per EN ISO 12944 C5-M and EN 60529	Use of device under water at a maximum water depth of: <ul style="list-style-type: none"> ▪ 3 m (10 ft): permanent use ▪ 10 m (30 ft): max. 48 hours
Order code for "Sensor option", Option CD, CE	IP68, Type 6P enclosure Fully welded, with protective coating as per EN ISO 12944 Im2/Im3 and EN 60529	Use of the device in buried applications, under water and in saline water at a maximum water depth of: <ul style="list-style-type: none"> ▪ 3 m (10 ft): permanent use ▪ 10 m (30 ft): max. 48 hours ▪ Use of device under water at a maximum water depth of: 10 m (30 ft): max. 48 hours ▪ Use of device in buried applications

Order code for "Sensor option", option CQ	IP68, type 6P, factory encapsulation Sensor with aluminum half-shell housing	Use of device under rainwater or surface water at a maximum water depth of: 3 m (10 ft)
Order code for "Sensor option", Option C3	IP66/67, type 4X enclosure Fully welded, with protective coating as per EN ISO 12944 C5-M	For operation in corrosive environment

Vibration resistance and shock resistance

Compact version

Vibration, sinusoidal Following IEC 60068-2-6	2 to 8.4 Hz	3.5 mm peak
	8.4 to 2 000 Hz	1 g peak
Vibration, broad-band random Following IEC 60068-2-64	10 to 200 Hz	0.003 g ² /Hz
	200 to 2 000 Hz	0.001 g ² /Hz (1.54 g rms)
Shocks, half-sine Following IEC 60068-2-27	6 ms 30 g	

Shock

Due to rough handling similar to IEC 60068-2-31.

Remote version (sensor)

Vibration, sinusoidal Following IEC 60068-2-6	2 to 8.4 Hz	7.5 mm peak
	8.4 to 2 000 Hz	2 g peak
Vibration, broad-band random Following IEC 60068-2-6	10 to 200 Hz	0.01 g ² /Hz
	200 to 2 000 Hz	0.003 g ² /Hz (2.7 g rms)
Shocks, half-sine Following IEC 60068-2-6	6 ms 50 g	

Shock

Due to rough handling similar to IEC 60068-2-31.

Electromagnetic compatibility (EMC)

As per IEC/EN 61326 and

- HART, Modbus RS485: NAMUR Recommendation NE 21
- IO-Link: IO-Link Interface and System Specification



For more information: Declaration of Conformity

Process

Medium temperature range	58
Conductivity	58
Flow limit	58
Pressure/temperature ratings	60
Pressure tightness	63
Pressure loss	63

Medium temperature range

The medium temperature range depends on the liner.

Hard rubber	0 to +80 °C (+32 to +176 °F)
Polyurethane	-20 to +50 °C (-4 to +122 °F)
PTFE	<ul style="list-style-type: none"> ■ Process connection, carbon steel: -10 to +90 °C (+14 to +194 °F) ■ Process connection, stainless steel: -20 to +90 °C (-4 to +194 °F)

Conductivity


The minimum conductivity is:

- 5 $\mu\text{S}/\text{cm}$ for liquids in general
- 20 $\mu\text{S}/\text{cm}$ for demineralized water

The following basic conditions must be observed for $< 20 \mu\text{S}/\text{cm}$:

- Order code 013 for "Functionality", option D "Extended transmitter" and higher output signal damping is recommended for values under 20 $\mu\text{S}/\text{cm}$.
- Observe the maximum permitted cable length L_{max} . This length is determined by the conductivity of the medium.
- With order code 013 "Functionality", option A "Standard transmitter" and empty pipe detection (EPD) switched on, the minimum conductivity is 20 $\mu\text{S}/\text{cm}$.
- With order code 013 "Functionality", option A "Standard transmitter" - remote version, empty pipe detection may not be activated if $L_{\text{max}} > 20 \text{ m}$.

i Note that in the case of the remote version, the minimum conductivity depends on the cable length.



10 Permitted length of connecting cable

Colored area = permitted range

L_{max} = length of connecting cable in [m] ([ft])

[$\mu\text{S}/\text{cm}$] = medium conductivity

Red line = order code 013 "Functionality", option A "Standard transmitter"

Blue line = order code 013 "Functionality", option D "Extended transmitter"

Flow limit

Pipe diameter and flow rate determine the nominal diameter of the sensor.

i The flow velocity is increased by reducing the sensor nominal diameter.

2 to 3 m/s (6.56 to 9.84 ft/s)	Optimum flow velocity
$v < 2$ m/s (6.56 ft/s)	For abrasive media, e.g. potter's clay, lime milk, ore slurry
$v > 2$ m/s (6.56 ft/s)	For media producing buildup, e.g. wastewater sludge


Pressure/temperature ratings

Maximum permitted medium pressure as a function of the medium temperature

The data relate to all pressure-bearing parts of the device.

Fixed flange similar to EN 1092-1


Stainless steel (-20 °C (-4 °F))
Carbon steel (-10 °C (14 °F))



A0038122-EN


Fixed flange similar to ASME B16.5

Stainless steel



A0038123-EN


Carbon steel



A0038121-EN

Fixed flange similar to JIS B2220


Stainless steel (-20 °C (-4 °F))
 Carbon steel (-10 °C (14 °F))



A0038124-EN

Fixed flange similar to AWWA C207


Carbon steel



A0038126-EN

Fixed flange similar to AS 2129


Carbon steel



A0038127-EN

Fixed flange similar to AS 4087


Carbon steel



A0038128-EN

Lap joint flange/lap joint flange, stamped plate similar to EN 1092-1 and ASME B16.5

Stainless steel (-20 °C (-4 °F))
Carbon steel (-10 °C (14 °F))



A0038129-EN

- 1 Lap joint flange PN16/Class 150
- 2 Lap joint flange, stamped plate PN10, lap joint flange PN10

Pressure tightness

Limit values for the absolute pressure depending on the liner and medium temperature

PTFE	Nominal diameter		Absolute pressure in [mbar] ([psi])	
	[mm]	[in]	+25 °C (+77 °F)	+90 °C (+194 °F)
	25	1	0 (0)	0 (0)
	40	2	0 (0)	0 (0)
	50	2	0 (0)	0 (0)
	65	2 ½	0 (0)	40 (0.58)
	80	3	0 (0)	40 (0.58)
	100	4	0 (0)	135 (2.0)
	125	5	135 (2.0)	240 (3.5)
	150	6	135 (2.0)	240 (3.5)
	200	8	200 (2.9)	290 (4.2)
	250	10	330 (4.8)	400 (5.8)
	300	12	400 (5.8)	500 (7.3)

Hard rubber	+25 °C (+77 °F)	+50 °C (+122 °F)	+80 °C (+176 °F)
	0 (0)	0 (0)	0 (0)

Polyurethane	+25 °C (+77 °F)	+50 °C (+122 °F)
	0 (0)	0 (0)

Pressure loss

- No pressure loss: transmitter installed in a pipe with the same nominal diameter.
- Pressure loss information when adapters are used → *Adapters*, 50

Mechanical construction

Weight	66
Measuring tube specification in SI units	69
Measuring tube specification in US units	70
Materials	72
Fitted electrodes	73
Process connections	73
Surface roughness	73

Weight

All values refer to devices with flanges with a standard pressure rating.
Weight data are guideline values. The weight may be lower than indicated depending on the pressure rating and design.

Transmitter remote version

- Polycarbonate: 1.4 kg (3.1 lbs)
- Aluminum: 2.4 kg (5.3 lbs)

Sensor remote version

Aluminum sensor connection housing: see the information in the following table.

Weight in SI units

Order code for "Design", options D, E, H, I	Nominal diameter		EN (DIN), AS, JIS		ASME (Class 150)
	[mm]	[in]	Pressure rating	[kg]	[kg]
	25	1	PN 40	10	5
	32	–	PN 40	11	–
	40	1 ½	PN 40	12	7
	50	2	PN 40	13	9
	65	–	PN 16	13	–
	80	3	PN 16	15	14
	100	4	PN 16	18	19
	125	–	PN 16	25	–
	150	6	PN 16	31	33
	200	8	PN 10	52	52
	250	10	PN 10	81	90
	300	12	PN 10	95	129
	350	14	PN 6	106	172
	375	15	PN 6	121	–
	400	16	PN 6	121	203

Order code for "Design", options G, K	Nominal diameter		EN (DIN) (PN 6)	ASME (Class 150), AWWA (Class D)
	[mm]	[in]	[kg]	[kg]
	450	18	161	255
	500	20	156	285
	600	24	208	405
	700	28	304	400
	–	30	–	460
	800	32	357	550
	900	36	485	800
	1000	40	589	900
	–	42	–	1 100
	1200	48	850	1 400
	–	54	850	2 200
	1400	–	1 300	–
	–	60	–	2 700

Order code for "Design", options G, K	Nominal diameter		EN (DIN) (PN 6)	ASME (Class 150), AWWA (Class D)
	[mm]	[in]	[kg]	[kg]
	1600	-	1845	-
	-	66	-	3700
	1800	72	2357	4100
	-	78	2929	4600
	2000	-	2929	-

Order code for "Design", options F, J	Nominal diameter		EN (DIN) (PN16)	AS (PN 16)	ASME (Class 150), AWWA (Class D)
	[mm]	[in]	[kg]	[kg]	[kg]
	450	18	142	138	191
	500	20	182	186	228
	600	24	227	266	302
	700	28	291	369	266
	-	30	-	447	318
	800	32	353	524	383
	900	36	444	704	470
	1000	40	566	785	587
	-	42	-	-	670
	1200	48	843	1229	901
	-	54	-	-	1273
	1400	-	1204	-	-
	-	60	-	-	1594
	1600	-	1845	-	-
	-	66	-	-	2131
	1800	72	2357	-	2568
	-	78	2929	-	3113
	2000	-	2929	-	3113
	-	84	-	-	3755
	2200	-	3422	-	-
	-	90	-	-	4797
	2400	-	4094	-	-

Weight in US units

All values refer to devices with flanges with a standard pressure rating.
Weight data are guideline values. The weight may be lower than indicated depending on the pressure rating and design.

Transmitter remote version

- Polycarbonate: 3.1 lb
- Aluminum: 5.3 lb

Sensor remote version

Aluminum sensor connection housing: see the information in the following table.

Order code for "Design", options D, E, H, I	Nominal diameter		ASME (Class 150)
	[mm]	[in]	[lb]
	25	1	11
	32	–	–
	40	1 ½	15
	50	2	20
	65	–	–
	80	3	31
	100	4	42
	125	–	–
	150	6	73
	200	8	115
	250	10	198
	300	12	284
	350	14	379
	375	15	–
	400	16	448

Order code for "Design", options F, J	Nominal diameter		ASME (Class 150), AWWA (Class D)
	[mm]	[in]	[lb]
	450	18	421
	500	20	503
	600	24	666
	700	28	587
	–	30	701
	800	32	845
	900	36	1036
	1000	40	1294
	–	42	1477
	1200	48	1987
	–	54	2807
	1400	–	–
	–	60	3 515
	1600	–	–
	–	66	4 699
	1800	72	5 662

Order code for "Design", options F, J	Nominal diameter		ASME (Class 150), AWWA (Class D)
	[mm]	[in]	[lb]
-	78	-	6864
2000	-	-	6864
-	84	-	8280
2200	-	-	-
-	90	-	10577
2400	-	-	-

Order code for "Design", options G, K	Nominal diameter		ASME (Class 150), AWWA (Class D)
	[mm]	[in]	[lb]
450	18	-	562
500	20	-	628
600	24	-	893
700	28	-	882
-	30	-	1014
800	32	-	1213
900	36	-	1764
1000	40	-	1984
-	42	-	2426
1200	48	-	3087
-	54	-	4851
1400	-	-	-
-	60	-	5954
1600	-	-	-
-	66	-	8158
1800	72	-	9040
-	78	-	10143
2000	-	-	-

Measuring tube specification in SI units

Nominal diameter		EN (DIN)	Pressure rating			Measuring tube internal diameter		
[mm]	[in]		ASME	AS 2129	JIS	Hard rubber	Polyurethane	PTFE
		AWWA	AS 4087		[mm]	[mm]	[mm]	
25	1	PN 40	Class 150	-	20K	-	24	25
32	-	PN 40	-	-	20K	-	32	34
40	1 ½	PN 40	Class 150	-	20K	-	38	40
50	2	PN 40	Class 150	Table E, PN 16	10K	50	50	52
65	-	PN 16	-	-	10K	66	66	68
80	3	PN 16	Class 150	Table E, PN 16	10K	79	79	80
100	4	PN 16	Class 150	Table E, PN 16	10K	102	102	104

Nominal diameter		Pressure rating				Measuring tube internal diameter		
		EN (DIN)	ASME AWWA	AS 2129 AS 4087	JIS	Hard rubber	Polyurethane	PTFE
[mm]	[in]					[mm]	[mm]	[mm]
125	-	PN 16	-	-	10K	127	127	130
150	6	PN 16	Class 150	Table E, PN 16	10K	156	156	156
200	8	PN 10	Class 150	Table E, PN 16	10K	204	204	202
250	10	PN 10	Class 150	Table E, PN 16	10K	258	258	256
300	12	PN 10	Class 150	Table E, PN 16	10K	309	309	306
350	14	PN 6	Class 150	Table E, PN 16	10K	337	342	-
375	15	-	-	PN 16	10K	389	-	-
400	16	PN 6	Class 150	Table E, PN 16	10K	387	392	-
450	18	PN 6	Class 150	-	10K	436	437	-
500	20	PN 6	Class 150	Table E, PN 16	10K	487	492	-
600	24	PN 6	Class 150	Table E, PN 16	10K	589	594	-
700	28	PN 6	Class D	Table E, PN 16	10K	688	692	-
750	30	-	Class D	Table E, PN 16	10K	737	742	-
800	32	PN 6	Class D	Table E, PN 16	-	788	794	-
900	36	PN 6	Class D	Table E, PN 16	-	889	891	-
1000	40	PN 6	Class D	Table E, PN 16	-	991	994	-
-	42	-	Class D	-	-	1043	1043	-
1200	48	PN 6	Class D	Table E, PN 16	-	1191	1197	-
-	54	-	Class D	-	-	1339	-	-
1400	-	PN 6	-	-	-	1402	-	-
-	60	-	Class D	-	-	1492	-	-
1600	-	PN 6	-	-	-	1600	-	-
-	66	-	Class D	-	-	1638	-	-
1800	72	PN 6	-	-	-	1786	-	-
-	78	-	Class D	-	-	1989	-	-
-	84	-	Class D	-	-	2099	-	-
2200	-	PN 6	-	-	-	2194	-	-
-	90	-	Class D	-	-	2246	-	-
2400	-	PN 6	-	-	-	2391	-	-



Measuring tube specification in US units

Nominal diameter		Pressure rating	Measuring tube internal diameter			
[mm]	[in]	ASME AWWA	Hard rubber	Polyethylene	Polyurethane	PTFE
			[in]	[in]	[in]	[in]
25	1	Class 150	-		0.94	0.98
40	1 ½	Class 150	-		1.50	1.57

Nominal diameter		Pressure rating	Measuring tube internal diameter			
		ASME AWWA	Hard rubber	Polyethylene	Polyurethane	PTFE
[mm]	[in]		[in]	[in]	[in]	[in]
50	2	Class 150	1.97		1.97	2.05
80	3	Class 150	3.11		3.11	3.15
100	4	Class 150	4.02		4.02	4.09
150	6	Class 150	6.14		6.14	6.14
200	8	Class 150	8.03		8.03	7.95
250	10	Class 150	10.2		10.2	10.08
300	12	Class 150	12.2		12.2	12.05
350	14	Class 150	13.3	-	13.5	-
375	15	-	15.3	-	-	-
400	16	Class 150	15.2	-	15.4	-
450	18	Class 150	17.1	-	17.2	-
500	20	Class 150	19.1	-	19.4	-
600	24	Class 150	23.0	-	23.4	-
700	28	Class D	27.1	-	27.2	-
750	30	Class D	29.1	-	29.2	-
800	32	Class D	31.0	-	31.3	-
900	36	Class D	35.0	-	35.1	-
1000	40	Class D	39.0	-	39.1	-
-	42	Class D	41.1	-	41.1	-
1200	48	Class D	46.9	-	47.1	-
-	54	Class D	52.7	-	-	-
-	60	Class D	58.7	-	-	-
-	66	Class D	64.5	-	-	-
1800	72	-	70.3	-	-	-
-	78	Class D	78.3	-	-	-
-	84	Class D	84.0	-	-	-
-	90	Class D	89.8	-	-	-

Materials

Transmitter housing	
Order code for "Housing"	<ul style="list-style-type: none"> ■ Option A: Compact, coated aluminum ■ Option N: Remote, polycarbonate ■ Option P: Remote, aluminum, coated
Window material	<ul style="list-style-type: none"> ■ Order code for "Housing", option A: glass ■ Order code for "Housing", option N: polycarbonate ■ Order code for "Housing", option P: glass
Neck adapter	Order code for "Housing", option A, : Aluminum, coated
Sensor connection housing	
	<ul style="list-style-type: none"> ■ Aluminum, AlSi10Mg, coated (in conjunction with order code for "Sensor option", options CF, CQ, C3) ■ Polycarbonate (in conjunction with order code for "Sensor option", options CB, CC, CD, CE)
Cable glands and entries	
Cable gland M20×1.5	Plastic
Adapter for cable entry with G ½" or NPT ½" female thread	Nickel-plated brass
Connecting cable for remote version	
	Electrode cable and coil current cable: <ul style="list-style-type: none"> ■ PVC cable with copper shield ■ Reinforced cable: PVC cable with copper shield and additional steel wire braided jacket
Sensor housing	
DN 25 to 300 (1 to 12")	<ul style="list-style-type: none"> ■ Aluminum half-shell housing: aluminum, AlSi10Mg, coated ■ Fully welded carbon steel housing with protective varnish
DN 350 to 3 000 (14 to 120")	Fully welded carbon steel housing with protective varnish
Measuring tubes	
DN 25 to 600 (1 to 24")	Stainless steel: 1.4301, 1.4306, 304, 304L
DN 700 to 3 000 (28 to 120")	Stainless steel: 1.4301, 304, S30408, or equivalent
Liner	
DN 25 to 300 (1 to 12")	PTFE
DN 25 to 1 200 (1 to 48")	Polyurethane
DN 50 to 3 000 (2 to 120")	Hard rubber
Electrodes	
	<ul style="list-style-type: none"> ■ Stainless steel: 1.4435 (316L) ■ Alloy C22, 2.4602 (UNS N06022)
Seals	
	As per DIN EN 1514-1, Form IBC

Process connections	
EN 1092-1 (DIN 2501)	<p> For flanges made of carbon steel:</p> <ul style="list-style-type: none"> ▪ DN ≤ 300 (12"): with Al/Zn protective coating or protective varnish ▪ DN ≥ 350 (14"): protective varnish <p> All carbon steel lap joint flanges are supplied with a hot-dip galvanized finish.</p> <p>Fixed flange</p> <ul style="list-style-type: none"> ▪ Carbon steel: <ul style="list-style-type: none"> ▪ DN ≤ 300: S235JRG2, S235JR+N, P245GH, A105, E250C ▪ DN 350 to 3 000: P245GH, S235JRG2, A105, E250C ▪ Stainless steel: <ul style="list-style-type: none"> ▪ DN ≤ 300: 1.4404, 1.4571, F316L ▪ DN 350 to 600: 1.4571, F316L, 1.4404 ▪ DN 700 to 1 000: 1.4404, F316L <p>Lap joint flange</p> <ul style="list-style-type: none"> ▪ Carbon steel DN ≤ 300: S235JRG2, A105, E250C ▪ Stainless steel DN ≤ 300: 1.4306, 1.4404, 1.4571, F316L <p>Lap joint flange, stamped plate</p> <ul style="list-style-type: none"> ▪ Carbon steel DN ≤ 300: S235JRG2 similar to S235JR+AR or 1.0038 ▪ Stainless steel DN ≤ 300: 1.4301 similar to 304
ASME B16.5	<ul style="list-style-type: none"> ▪ Carbon steel: A105 ▪ Stainless steel: F316L
JIS B2220	<ul style="list-style-type: none"> ▪ Carbon steel: A105, A350 LF2 ▪ Stainless steel: F316L
AWWA C207	Carbon steel: A105, P265GH, A181 Class 70, E250C, S275JR
AS 2129	Carbon steel: A105, E250C, P235GH, P265GH, S235JRG2
AS 4087	Carbon steel: A105, P265GH, S275JR
Accessories	
Weather protection cover	Stainless steel, 1.4404 (316L)
Pipe mounting kit (welding jig)	Stainless steel 1.4301 (304)
Wall mounting kit	Stainless steel 1.4301 (304)
Ground disks	15 to 1 200 mm (½ to 48 in) <ul style="list-style-type: none"> ▪ Stainless steel, 1.4435 (316L) ▪ Alloy C22, 2.4602 (UNS N06022)

Fitted electrodes

- Standard electrodes:
- Measuring electrodes
 - Reference electrodes
 - Empty pipe detection electrodes

Process connections

- EN 1092-1 (DIN 2501)
- ASME B16.5
- JIS B2220
- AS 2129 Table E
- AS 4087 PN 16
- AWWA C207 Class D

Surface roughness

All data relate to parts in contact with medium.

Electrodes with 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); tantalum:
< 0.5 μm (19.7 μin)

Dimensions in SI units


Compact version	76
DN 25 to 300 (1 to 12")	76
DN 350 to 900 (14 to 36")	78
DN 1000 to 3000 (40 to 120")	80
Remote version	82
Transmitter remote version	82
Sensor connection housing	82
DN 25 to 300 (1 to 12") aluminum half-shell housing	83
DN 25 to 300 (1 to 12") fully welded housing	84
DN 350 to 900 (14 to 36")	85
DN 1000 to 3000 (40 to 120")	86
Fixed flange	87
Flange similar to EN 1092-1: PN 10	87
Flange similar to EN 1092-1: PN 16	88
Flange similar to EN 1092-1: PN 25	89
Flange similar to EN 1092-1: PN 40	90
Flange similar to ASME B16.5, Class 150	91
Flange similar to ASME B16.5, Class 300	92
Flange similar to JIS B2220, 10K	93
Flange similar to JIS B2220, 20K	94
Flange similar to AWWA, Class D	95
Flange similar to AS 2129, Tab. E	96
Flange according to AS 4087, PN 16	97
Lap joint flange	98
Lap joint flange similar to EN 1092-1: PN 10	98
Lap joint flange similar to EN 1092-1: PN 16	99
Lap joint flange similar to ASME B16.5, Class 150	100
Lap joint flange, stamped plate	101
Lap joint flange, stamping plate similar to EN 1092-1: PN 10	101
Accessories	102
Weather protection cover	102
Ground disks for flanges	102

Compact version

DN 25 to 300 (1 to 12")

Order code for "Housing", option A "Compact, aluminum, coated"

Sensor with aluminum half-shell housing



A0042708

DN		Order code for "Design"					
		A ¹⁾	B	Options D, E, H, I			L ³⁾
[mm]	[in]	[mm]	[mm]	C ²⁾	D ²⁾	E ²⁾	[mm]
25	1	139	178	258	84	120	200
32	–	139	178	258	84	120	200
40	1 ½	139	178	258	84	120	200
50	2	139	178	258	84	120	200
65	–	139	178	283	109	180	200
80	3	139	178	283	109	180	200
100	4	139	178	283	109	180	250
125	–	139	178	323	150	260	250
150	6	139	178	323	150	260	300
200	8	139	178	348	180	324	350
250	10	139	178	373	205	400	450
300	12	139	178	398	230	460	500


1) Depending on the cable entry used: values up to + 30 mm

2) Reference values: depending on the pressure rating, design and order option

3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

Order code for "Housing", option M "Compact, polycarbonate"

Sensor with aluminum half-shell housing



A0042708

DN		Order code for "Design"					
		Options D, E, H, I					
[mm]	[in]	A ¹⁾ [mm]	B [mm]	C ²⁾ [mm]	D ²⁾ [mm]	E ²⁾ [mm]	L ³⁾ [mm]
25	1	132	172	255	84	120	200
32	-	132	172	255	84	120	200
40	1 ½	132	172	255	84	120	200
50	2	132	172	255	84	120	200
65	-	132	172	280	109	180	200
80	3	132	172	280	109	180	200
100	4	132	172	280	109	180	250
125	-	132	172	320	150	260	250
150	6	132	172	320	150	260	300
200	8	132	172	345	180	324	350
250	10	132	172	370	205	400	450
300	12	132	172	395	230	460	500


1) Depending on the cable entry used: values up to + 30 mm

2) Reference values: depending on the pressure rating, design and order option

3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

DN 350 to 900 (14 to 36")

Order code for "Housing", option A "Compact, aluminum, coated"




A0042708

DN		Order code for "Design"									L ³⁾ [mm]	
		A ¹⁾ [mm]	B [mm]	Options E, F			Option G					
[mm]	[in]			C ²⁾ [mm]	D ²⁾ [mm]	E ²⁾ [mm]	C ²⁾ [mm]	D ²⁾ [mm]	E ²⁾ [mm]			
350	14	139	178	457	245	490	-	-	-		550	
375	15	139	178	483	271	542	-	-	-		600	
400	16	139	178	483	271	542	-	-	-		600	
450	18	139	178	465	299	598	508	333	666	600 ⁴⁾	650 ⁵⁾	
500	20	139	178	490	324	648	534	359	717	600 ⁴⁾	650 ⁵⁾	
600	24	139	178	540	365	730	586	411	821	600 ⁴⁾	780 ⁵⁾	
700	28	139	178	601	430	860	688	512	1024	700 ⁴⁾	910 ⁵⁾	
750	30	139	178	639	467	934	688	512	1024	750 ⁴⁾	975 ⁵⁾	
800	32	139	178	658	486	972	709	534	1065	800 ⁴⁾	1040 ⁵⁾	
900	36	139	178	708	536	1072	786	610	1218	900 ⁴⁾	1170 ⁵⁾	

- 1) Depending on the cable entry used: values up to + 30 mm
- 2) Reference values: depending on the pressure rating, design and order option
- 3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 4) Order code for "Design", option F "Fixed flange, short installed length"
- 5) Order code for "Design", option G "Fixed flange, long installed length"

Order code for "Housing", option M "Compact, polycarbonate"




A0042708

DN		Order code for "Design"									L ³⁾ [mm]	
		A ¹⁾ [mm]	B [mm]	Options E, F			Option G					
				C ²⁾ [mm]	D ²⁾ [mm]	E ²⁾ [mm]	C ²⁾ [mm]	D ²⁾ [mm]	E ²⁾ [mm]			
[mm]	[in]											
350	14	132	172	454	245	490	-	-	-		550	
375	15	132	172	480	271	542	-	-	-		600	
400	16	132	172	480	271	542	-	-	-		600	
450	18	132	172	462	299	598	505	333	666	600 ⁴⁾	650 ⁵⁾	
500	20	132	172	487	324	648	531	359	717	600 ⁴⁾	650 ⁵⁾	
600	24	132	172	537	365	730	583	411	821	600 ⁴⁾	780 ⁵⁾	
700	28	132	172	598	430	860	685	512	1024	700 ⁴⁾	910 ⁵⁾	
750	30	132	172	636	467	934	685	512	1024	750 ⁴⁾	975 ⁵⁾	
800	32	132	172	655	486	972	706	534	1065	800 ⁴⁾	1040 ⁵⁾	
900	36	132	172	705	536	1072	783	610	1218	900 ⁴⁾	1170 ⁵⁾	

- 1) Depending on the cable entry used: values up to + 30 mm
- 2) Reference values: depending on the pressure rating, design and order option
- 3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 4) Order code for "Design", option F "Fixed flange, short installed length"
- 5) Order code for "Design", option G "Fixed flange, long installed length"

DN 1000 to 3000 (40 to 120")

Order code for "Housing", option A "Compact, aluminum, coated"



A0042708

DN		A ¹⁾	B	C ²⁾	D ²⁾	E ²⁾	L ³⁾	
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	
1000	40	139	178	759	582	1164	1000 ⁴⁾	1300 ⁵⁾
-	42	139	178	795	618	1236	1050 ⁴⁾	1365 ⁵⁾
1200	48	139	178	873	696	1392	1200 ⁴⁾	1560 ⁵⁾
-	54	139	178	986	809	1617	1350 ⁴⁾	1755 ⁵⁾
1400	-	139	178	986	809	1617	1400 ⁴⁾	1820 ⁵⁾
-	60	139	178	1086	909	1817	1500 ⁴⁾	1950 ⁵⁾
1600	-	139	178	1086	909	1817	1600 ⁴⁾	2080 ⁵⁾
-	66	139	178	1137	960	1919	1650 ⁴⁾	2145 ⁵⁾
1800	72	139	178	1193	1016	2032	1800 ⁴⁾	2340 ⁵⁾
-	78	139	178	1305	1127	2254	2000 ⁴⁾	2600 ⁵⁾
2000	-	139	178	1305	1127	2254	2000 ⁴⁾	2600 ⁵⁾
-	84	139	178	1405	1227	2454	2150 ⁴⁾	
2200	-	139	178	1405	1227	2454	2200 ⁴⁾	
-	90	139	178	1510	1227	2664	2300 ⁴⁾	
2400	-	139	178	1510	1332	2664	2400 ⁴⁾	
-	96	139	178	1609	1431	2861	2450 ⁴⁾	
-	102	139	178	1694	1516	3032	2600 ⁴⁾	
2600	-	139	178	1620	1442	2883	2600 ⁴⁾	
-	108	139	178	1781	1602	3204	2750 ⁴⁾	
2800	-	139	178	1725	1547	3093	2800 ⁴⁾	
-	114	139	178	1866	1688	3375	2900 ⁴⁾	
3000	-	139	178	1825	1647	3293	3000 ⁴⁾	
-	120	139	178	1952	1774	3547	3050 ⁴⁾	

1) Depending on the cable entry used: values up to + 30 mm


2) Reference values: depending on the pressure rating, design and order option

3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

4) Order code for "Design", option F "Fixed flange, short installed length"

5) Order code for "Design", option G "Fixed flange, long installed length"

Order code for "Housing", option M "Compact, polycarbonate"




A0042708

DN		A ¹⁾	B	C ²⁾	D ²⁾	E ²⁾	L ³⁾	
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	
1000	40	132	172	756	582	1164	1000 ⁴⁾	1300 ⁵⁾
-	42	132	172	792	618	1236	1050 ⁴⁾	1365 ⁵⁾
1200	48	132	172	870	696	1392	1200 ⁴⁾	1560 ⁵⁾
-	54	132	172	983	809	1617	1350 ⁴⁾	1755 ⁵⁾
1400	-	132	172	983	809	1617	1400 ⁴⁾	1820 ⁵⁾
-	60	132	172	1083	909	1817	1500 ⁴⁾	1950 ⁵⁾
1600	-	132	172	1083	909	1817	1600 ⁴⁾	2080 ⁵⁾
-	66	132	172	1134	960	1919	1650	2145 ⁵⁾
1800	72	132	172	1190	1016	2032	1800 ⁴⁾	2340 ⁵⁾
-	78	132	172	1302	1127	2254	2000 ⁴⁾	2600 ⁵⁾
2000	-	132	172	1302	1127	2254	2000 ⁴⁾	2600 ⁵⁾
-	84	132	172	1402	1227	2454	2150 ⁴⁾	
2200	-	132	172	1402	1227	2454	2200 ⁴⁾	
-	90	132	172	1507	1227	2664	2300 ⁴⁾	
2400	-	132	172	1507	1332	2664	2400 ⁴⁾	
-	96	132	172	1606	1431	2861	2450 ⁴⁾	
-	102	132	172	1691	1516	3032	2600 ⁴⁾	
2600	-	132	172	1617	1442	2883	2600 ⁴⁾	
-	108	132	172	1778	1602	3204	2750 ⁴⁾	
2800	-	132	172	1722	1547	3093	2800 ⁴⁾	
-	114	132	172	1863	1688	3375	2900 ⁴⁾	
3000	-	132	172	1822	1647	3293	3000 ⁴⁾	
-	120	132	172	1949	1774	3547	3050 ⁴⁾	

- 1) Depending on the cable entry used: values up to + 30 mm
- 2) Reference values: depending on the pressure rating, design and order option
- 3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 4) Order code for "Design", option F "Fixed flange, short installed length"
- 5) Order code for "Design", option G "Fixed flange, long installed length"

Remote version

Transmitter remote version




A0042715

Order code for "Housing"	A ¹⁾ [mm]	B [mm]	C [mm]	D [mm]	E [mm]
Option N "Remote, polycarbonate"	132	187	172	307	130
Option P and T "Remote, coated aluminum"	139	185	178	309	130

1) Depending on the cable entry used: values up to + 30 mm

Sensor connection housing



A0042716


Housing material	A ¹⁾ [mm]	B [mm]
Polycarbonate plastic ²⁾	113	112
Aluminum, coated ³⁾	148	136

- 1) Depending on the cable entry used: values up to + 30 mm
- 2) In conjunction with order code for "Sensor option", options CB, CC, CD, CE
- 3) In conjunction with order code for "Sensor option", options CF, CQ, C3

DN 25 to 300 (1 to 12") aluminum half-shell housing

Sensor with aluminum half-shell housing.

Sensor connection housing: aluminum, AlSi10Mg, coated




A0041519

DN		Order code for "Design"			
		Options D, E, H, I			
[mm]	[in]	C ¹⁾ [mm]	D [mm]	E [mm]	L ²⁾ [mm]
25	1	197	84	120	200
32	-	197	84	120	200
40	1 ½	197	84	120	200
50	2	197	84	120	200
65	-	222	109	180	200
80	3	222	109	180	200
100	4	222	109	180	250
125	-	262	150	260	250
150	6	262	150	260	300
200	8	287	180	324	350
250	10	312	205	400	450
300	12	337	230	460	500

- 1) Reference values: depending on the pressure rating, design and order option
- 2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

DN 25 to 300 (1 to 12") fully welded housing

Sensor with fully welded carbon steel housing:
Order code for "Sensor option", options CB, CC, CD, CE




A0041519

DN		Order code for "Design"			
		Options A, E			
[mm]	[in]	C ¹⁾ [mm]	D ¹⁾ [mm]	E ¹⁾ [mm]	L ²⁾ [mm]
25	1	189	70	140	200
32	-	189	70	140	200
40	1 ½	189	70	140	200
50	2	189	70	140	200
65	-	202	82	165	200
80	3	207	87	175	200
100	4	219	100	200	250
125	-	232	113	226	250
150	6	254	134	269	300
200	8	279	160	320	350
250	10	313	193	387	450
300	12	338	218	437	500

1) Reference values: depending on the pressure rating, design and order option

2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

DN 350 to 900 (14 to 36")




A0041519

DN		Order code for "Design"							L ²⁾ [mm]	
		Options E, F			Option G					
[mm]	[in]	C ¹⁾ [mm]	D ¹⁾ [mm]	E ¹⁾ [mm]	C ¹⁾ [mm]	D ¹⁾ [mm]	E ¹⁾ [mm]			
350	14	395	245	490	-	-	-	550		
375	15	421	271	542	-	-	-	600		
400	16	421	271	542	-	-	-	600		
450	18	403	299	598	446	333	666	600 ³⁾	650 ⁴⁾	
500	20	428	324	648	472	359	717	600 ³⁾	650 ⁴⁾	
600	24	478	365	730	524	411	821	600 ³⁾	780 ⁴⁾	
700	28	539	430	860	626	512	1024	700 ³⁾	910 ⁴⁾	
750	30	577	467	934	626	512	1024	750 ³⁾	975 ⁴⁾	
800	32	596	486	972	647	534	1065	800 ³⁾	1040 ⁴⁾	
900	36	646	536	1072	724	610	1218	900 ³⁾	1170 ⁴⁾	

- 1) Reference values: depending on the pressure rating, design and order option
- 2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 3) Order code for "Design", option F "Fixed flange, short installed length"
- 4) Order code for "Design", option G "Fixed flange, long installed length"

DN 1000 to 3000 (40 to 120")



A0041519

DN		C ¹⁾	D ¹⁾	E ¹⁾	L ²⁾	
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	
1000	40	698	582	1164	1000 ³⁾	1300 ⁴⁾
-	42	734	618	1236	1050 ³⁾	1365 ⁴⁾
1200	48	812	696	1392	1200 ³⁾	1560 ⁴⁾
-	54	925	809	1617	1350 ³⁾	1755 ⁴⁾
1400	-	925	809	1617	1400 ³⁾	1820 ⁴⁾
-	60	1025	909	1817	1500 ³⁾	1950 ⁴⁾
1600	-	1025	909	1817	1600 ³⁾	2080 ⁴⁾
-	66	1076	960	1919	1650 ³⁾	2145 ⁴⁾
1800	72	1132	1016	2032	1800 ³⁾	2340 ⁴⁾
-	78	1244	1127	2254	2000 ³⁾	2600 ⁴⁾
2000	-	1244	1127	2254	2000 ³⁾	2600 ⁴⁾
-	84	1344	1227	2454	2150 ³⁾	
2200	-	1344	1227	2454	2200 ³⁾	
-	90	1449	1227	2664	2300 ³⁾	
2400	-	1449	1332	2664	2400 ³⁾	
-	96	1548	1431	2861	2450 ³⁾	
-	102	1633	1516	3032	2600 ³⁾	
2600	-	1559	1442	2883	2600 ³⁾	
-	108	1720	1602	3204	2750 ³⁾	
2800	-	1664	1547	3093	2800 ³⁾	
-	114	1805	1688	3375	2900 ³⁾	
3000	-	1764	1647	3293	3000 ³⁾	
-	120	1891	1774	3547	3050 ³⁾	

1) Reference values: depending on the pressure rating, design and order option

2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

3) Order code for "Design", option F "Fixed flange, short installed length"

4) Order code for "Design", option G "Fixed flange, long installed length"


Fixed flange

Flange similar to EN 1092-1: PN 10

- Carbon steel: order code for "Process connection", option D2K
- Stainless steel: order code for "Process connection", option D2S

Surface roughness: EN 1092-1 Form B1 (DIN 2526 Form C), Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
200	340	295	8 × Ø22	26
250	395	350	12 × Ø22	28
300	445	400	12 × Ø22	28
350	505	460	16 × Ø22	26
400	565	515	16 × Ø26	26
450	615	565	20 × Ø26	26
500	670	620	20 × Ø26	28
600	780	725	20 × Ø30	30
700	895	840	24 × Ø30	35
800	1015	950	24 × Ø33	38
900	1115	1050	28 × Ø33	38
1000	1230	1160	28 × Ø36	44
1200	1455	1380	32 × Ø39	55
1400	1675	1590	36 × Ø42	65
1600	1915	1820	40 × Ø48	75
1800	2115	2020	44 × Ø48	85
2000	2325	2230	48 × Ø48	90
2200	2550	2440	52 × Ø56	100
2400	2760	2650	56 × Ø56	110
2600	2960	2850	60 × Ø56	110
2800	3180	3070	64 × Ø56	124
3000	3405	3290	68 × Ø62	132

Flange similar to EN 1092-1: PN 16

- Carbon steel: order code for "Process connection", option D3K
- Stainless steel: order code for "Process connection", option D3S

Surface roughness: EN 1092-1 Form B1 (DIN 2526 Form C), Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
65	185	145	8 × Ø18	20
80	200	160	8 × Ø18	20
100	220	180	8 × Ø18	22
125	250	210	8 × Ø18	24
150	285	240	8 × Ø22	24
200	340	295	12 × Ø22	26
250	405	355	12 × Ø26	32
300	460	410	12 × Ø26	32
350	520	470	16 × Ø26	30
400	580	525	16 × Ø30	32
450	640	585	20 × Ø30	34
500	715	650	20 × Ø33	36
600	840	770	20 × Ø36	40
700	910	840	24 × Ø36	40
800	1025	950	24 × Ø39	41
900	1125	1050	28 × Ø39	48
1000	1255	1170	28 × Ø42	59
1200	1485	1390	32 × Ø48	78
1400	1685	1590	36 × Ø48	84
1600	1930	1820	40 × Ø56	102
1800	2130	2020	44 × Ø56	110
2000	2345	2230	48 × Ø62	124

Flange similar to EN 1092-1: PN 25

- Carbon steel: order code for "Process connection", option D4K
- Stainless steel: order code for "Process connection", option D4S

Surface roughness: EN 1092-1 Form B1 (DIN 2526 Form C), Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
200	360	310	12 × Ø26	32
250	425	370	12 × Ø30	36
300	485	430	16 × Ø30	40
350	555	490	16 × Ø33	38
400	620	550	16 × Ø36	40
450	670	600	20 × Ø36	46
500	730	660	20 × Ø36	48
600	845	770	20 × Ø39	48
700	960	875	24 × Ø42	50
800	1085	990	24 × Ø48	53
900	1185	1090	28 × Ø48	57
1000	1320	1210	28 × Ø56	63

Flange similar to EN 1092-1: PN 40

- Carbon steel: order code for "Process connection", option D5K
- Stainless steel: order code for "Process connection", option D5S

Surface roughness: EN 1092-1 Form B1 (DIN 2526 Form C), Ra 6.3 to 12.5 μm

E: Internal diameter depends on the liner \rightarrow *Measuring tube specification in SI units*, 69.



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
25	115	85	4 × Ø14	16
32	140	100	4 × Ø18	18
40	150	110	4 × Ø18	18
50	165	125	4 × Ø18	20
65	185	145	8 × Ø18	24
80	200	160	8 × Ø18	26
100	235	190	8 × Ø22	26
125	270	220	8 × Ø26	28
150	300	250	8 × Ø26	30

Flange similar to ASME B16.5, Class 150

- Carbon steel: order code for "Process connection", option A1K
- Stainless steel: order code for "Process connection", option A1S

Surface roughness: Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
25	108	79.2	4 × Ø16	12.6
40	127	98.6	4 × Ø16	15.9
50	152.4	120.7	4 × Ø19.1	17.5
80	190.5	152.4	4 × Ø19.1	22.3
100	228.6	190.5	8 × Ø19.1	22.3
150	279.4	241.3	8 × Ø22.4	23.8
200	342.9	298.5	8 × Ø22.4	26.8
250	406.4	362	12 × Ø25.4	29.6
300	482.6	431.8	12 × Ø25.4	30.2
350	535	476.3	12 × Ø28.6	35.4
400	595	539.8	16 × Ø28.6	37
450	635	577.9	16 × Ø31.8	40.1
500	700	635	20 × Ø31.8	43.3
600	815	749.3	20 × Ø34.9	48.1

Flange similar to ASME B16.5, Class 300

- Carbon steel: order code for "Process connection", option A2K
- Stainless steel: order code for "Process connection", option A2S

Surface roughness: Ra 6.3 to 12.5 μm

E: Internal diameter depends on the liner \rightarrow *Measuring tube specification in SI units*, 69



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
25	123.9	88.9	4 × Ø19.1	15.9
40	155.4	114.3	4 × Ø22.4	19
50	165.1	127	8 × Ø19.1	20.8
80	209.6	168.1	8 × Ø22.4	26.8
100	254	200.2	8 × Ø22.4	30.2
150	317.5	269.7	12 × Ø22.4	35

Flange similar to JIS B2220, 10K

- Carbon steel: order code for "Process connection", option N3K
- Stainless steel: order code for "Process connection", option N3S

Surface roughness: Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
50	155	120	4 × Ø19	16
65	175	140	4 × Ø19	18
80	185	150	8 × Ø19	18
100	210	175	8 × Ø19	18
125	250	210	8 × Ø23	20
150	280	240	8 × Ø23	22
200	330	290	12 × Ø23	22
250	400	355	12 × Ø25	24
300	445	400	16 × Ø25	24

Flange similar to JIS B2220, 20K

- Carbon steel: order code for "Process connection", option N4K
- Stainless steel: order code for "Process connection", option N4S

Surface roughness: Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
25	125	90	4 × Ø19	16
32	135	100	4 × Ø19	18
40	140	105	4 × Ø19	18
50	155	120	8 × Ø19	18
65	175	140	8 × Ø19	20
80	200	160	8 × Ø23	22
100	225	185	8 × Ø23	24
125	270	225	8 × Ø25	26
150	305	260	12 × Ø25	28
200	350	305	12 × Ø25	30
250	430	380	12 × Ø27	34
300	480	430	16 × Ø27	36

Flange similar to AWWA, Class D

Order code for "Process connection", option W1K

Surface roughness: Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69




A0041915

	DN		A [mm]	B [mm]	C [mm]	D [mm]
	[mm]	[in]				
	700	28	927	863.6	28 × Ø35	33.4
	750	30	984	914.4	28 × Ø35	35
	800	32	1060	977.9	28 × Ø42	38.1
	900	36	1168	1085.9	32 × Ø42	41.3
	1000	40	1289	1200.2	36 × Ø42	41.3
	-	42	1346	1257.3	36 × Ø42	44.5
	1200	48	1511	1422.4	44 × Ø42	47.7
	-	54	1683	1593.9	44 × Ø48	54
	-	60	1855	1759	52 × Ø48	57.2
	-	66	2032	1930.4	52 × Ø48	63.5
	1800	72	2197	2095.5	60 × Ø48	66.7
	-	78	2362	2260.6	64 × Ø54	69.9
	-	84	2535	2425.7	64 × Ø54	73.1
	-	90	2705	2717.8	68 × Ø60	76.2
	-	96	2877	2755.9	68 × Ø60.3	82.55
	-	102	3048	2908.3	68 × Ø66.7	82.55
	-	108	3219	3067.0	68 × Ø66.7	85.73
	-	114	3391	3219.5	68 × Ø73	88.90
	-	120	3562	3371.8	68 × Ø73	88.90

Flange similar to AS 2129, Tab. E

Order code for "Process connection", option M2K

Surface roughness: Ra 6.3 to 12.5 μm E: Internal diameter depends on the liner \rightarrow *Measuring tube specification in SI units*, 69.

A0041915


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
80	185	146	4 × Ø18	12
100	215	178	8 × Ø18	13
150	280	235	8 × Ø22	17
200	335	292	8 × Ø22	19
250	405	356	12 × Ø22	22
300	455	406	12 × Ø26	25
350	525	470	12 × Ø26	30
400	580	521	12 × Ø26	32
450	640	584	16 × Ø26	35
500	705	641	16 × Ø26	38
600	825	756	16 × Ø33	48
700	910	845	20 × Ø33	51
750	995	927	20 × Ø36	54
800	1060	984	20 × Ø36	54
900	1175	1092	24 × Ø36	64
1000	1255	1175	24 × Ø39	67
1200	1490	1410	32 × Ø39	79

Flange according to AS 4087, PN 16

Order code for "Process connection", option M3K

Surface roughness: Ra 6.3 to 12.5 µm

E: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0041915

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]
80	185	146	4 × Ø18	12
100	215	178	4 × Ø18	13
150	280	235	8 × Ø18	13
200	335	292	8 × Ø18	19
250	405	356	8 × Ø22	19
300	455	406	12 × Ø22	23
350	525	470	12 × Ø26	30
375	550	495	12 × Ø26	30
400	580	521	12 × Ø26	32
450	640	584	12 × Ø26	30
500	705	641	16 × Ø26	38
600	825	756	16 × Ø30	48
700	910	845	20 × Ø30	56
750	995	927	20 × Ø33	56
800	1060	984	20 × Ø36	56
900	1175	1092	24 × Ø36	66
1000	1255	1175	24 × Ø36	66
1200	1490	1410	32 × Ø36	76


Lap joint flange

Lap joint flange similar to EN 1092-1: PN 10

- Carbon steel: order code for "Process connection", option D22
- Stainless steel: order code for "Process connection", option D24

Surface roughness (flange): Ra 6.3 to 12.5 μm

F: Internal diameter depends on the liner \rightarrow *Measuring tube specification in SI units*, 69



A0042254


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]
200	340	295	8 × Ø22	24	264
250	395	350	12 × Ø22	26	317
300	445	400	12 × Ø22	26	367

Lap joint flange similar to EN 1092-1: PN 16

- Carbon steel: order code for "Process connection", option D32
- Stainless steel: order code for "Process connection", option D34

Surface roughness (flange): Ra 6.3 to 12.5 µm

F: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0042254


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]
25	115	85	4 × Ø14	16	49
32	140	100	4 × Ø18	18	65
40	150	110	4 × Ø18	18	71
50	165	125	4 × Ø18	20	88
65	185	145	8 × Ø18	20	103
80	200	160	8 × Ø18	20	120
100	220	180	8 × Ø18	22	148
125	250	210	8 × Ø18	22	177
150	285	240	8 × Ø22	24	209
200	340	295	12 × Ø22	26	264
250	405	355	12 × Ø26	29	317
300	460	410	12 × Ø26	32	367

Lap joint flange similar to ASME B16.5, Class 150

- Carbon steel: order code for "Process connection", option A12
- Stainless steel: order code for "Process connection", option A14

Surface roughness (flange): Ra 6.3 to 12.5 μm

F: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69



A0042254

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]
25	110	80	4 × Ø16	14	49
40	125	98	4 × Ø16	17.5	71
50	150	121	4 × Ø19	19	88
80	190	152	4 × Ø19	24	120
100	230	190	8 × Ø19	24	148
150	280	241	8 × Ø23	25	209
200	345	298	8 × Ø23	29	264
250	405	362	12 × Ø25	30	317
300	485	432	12 × Ø25	32	378


Lap joint flange, stamped plate

Lap joint flange, stamping plate similar to EN 1092-1: PN 10

- Carbon steel: order code for "Process connection", option D21
- Stainless steel: order code for "Process connection", option D23

Surface roughness (flange): Ra 6.3 to 12.5 µm

F: Internal diameter depends on the liner → *Measuring tube specification in SI units*, 69




A0042254

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]
25	115	85	4 x Ø13.5	16.5	49
32	140	100	4 x Ø17.5	17	65
40	150	110	4 x Ø17.5	16.5	71
50	165	125	4 x Ø17.5	18.5	88
65	185	145	4 x Ø17.5	20	103
80	200	160	8 x Ø17.5	23.5	120
100	220	180	8 x Ø17.5	24.5	148
125	250	210	8 x Ø17.5	24	177
150	285	240	8 x Ø21.5	25	209
200	340	295	8 x Ø21.5	27.5	264
250	405	350	12 x Ø21.5	30.5	317
300	445	400	12 x Ø21.5	34.5	367

Accessories

Weather protection cover




A0042332

A [mm]	B [mm]	D [mm]	E [mm]	F [mm]
257	12	280	140	140

Ground disks for flanges

DN 15 to 300 (½ to 12")		DN	Pressure rating	A	B	C ¹⁾	D	E	F
[mm]	[in]	[mm]		[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
		25	2)	87.5	6.5	2	26	62	77.5
		32	2)	94.5	6.5	2	35	80	87.5
		40	2)	103	6.5	2	41	82	101
		50	2)	108	6.5	2	52	101	115.5
		65	2)	118	6.5	2	68	121	131.5
		80	2)	135	6.5	2	80	131	154.5
		100	2)	153	6.5	2	104	156	186.5
		125	2)	160	6.5	2	130	187	206.5
		150	2)	184	6.5	2	158	217	256
		200	2)	205	6.5	2	206	267	288
		250	2)	240	6.5	2	260	328	359
		300	PN 10 PN 16 Cl. 150	273	6.5	2	312	375	413



A0042322

- 1) Material thickness
- 2) In the case of DN 25 to 250, ground disks can be used for all the flange standards/pressure ratings which can be supplied in the standard version.

DN 300 to 600 (12 to 24")		DN	Rating	A	B	C ¹⁾	D	E	F
		[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
		300	12"	268	9	2	310	375	404
		350	14"	365	9	2	343	420	479
		375	15"	395	9	2	393	461	523
		400	16"	395	9	2	393	470	542
		450	18"	417	9	2	439	525	583
		500	20"	460	9	2	493	575	650
		600	24"	522	9	2	593	676	766

A0042323

1) Material thickness

DN 700 to 1200 (28 to 48")		DN	Pressure rating	A	B	C ¹⁾	D	E
		[mm]	[inch]	[mm]	[mm]	[mm]	[mm]	[mm]
		700	28"	460 480 490 494	6.4	2	697 693 687 693	786 813 807 832
		750	30"	523	6.4	2	743	883
		800	32"	520 540 550 561	6.4	2	799 795 789 795	893 920 914 940
		900	36"	570 590 595 615	6.4	2	897 893 886 893	993 1020 1014 1048
		1000	40"	620 650 660 675	6.4	2	999 995 988 995	1093 1127 1131 1163
		-	42"	704	6.4	2	1044 1044	1220
		1200	48"	733 760 775 786	6.4	2	1203 1196 1188 1196	1310 1344 1345 1385

A0042324

1) Material thickness



Dimensions in US units


Compact version	106
DN 25 to 300 (1 to 12")	106
DN 350 to 900 (14 to 36")	108
DN 1000 to 3000 (40 to 120")	110
Remote version	112
Transmitter remote version	112
Sensor connection housing	112
DN 25 to 300 (1 to 12") aluminum half-shell housing	113
DN 25 to 300 (1 to 12") fully welded housing	114
DN 350 to 900 (14 to 36")	115
DN 1000 to 3000 (40 to 120")	116
Fixed flange	117
Flange similar to ASME B16.5, Class 150	117
Flange similar to ASME B16.5, Class 300	117
Flange similar to AWWA, Cl. D	118
Lap joint flange	119
Lap joint flange similar to ASME B16.5, Class 150	119
Accessories	120
Weather protection cover	120
Ground disks for flanges	120

Compact version

DN 25 to 300 (1 to 12")

Order code for "Housing", option A "Compact, aluminum, coated"

Sensor with aluminum half-shell housing



A0042708

DN		A ¹⁾ [in]	B [in]	Order code for "Design"			L ³⁾ [in]
[mm]	[in]			Options D, E, H, I			
			C ²⁾ [in]	D ²⁾ [in]	E ²⁾ [in]		
25	1	5.47	7.01	10.16	3.31	4.72	7.87
32	–	5.47	7.01	10.16	3.31	4.72	7.87
40	1 ½	5.47	7.01	10.16	3.31	4.72	7.87
50	2	5.47	7.01	10.16	3.31	4.72	7.87
65	–	5.47	7.01	11.14	4.29	7.09	7.87
80	3	5.47	7.01	11.14	4.29	7.09	7.87
100	4	5.47	7.01	11.14	4.29	7.09	9.84
125	–	5.47	7.01	12.72	5.91	10.24	9.84
150	6	5.47	7.01	12.72	5.91	10.24	11.81
200	8	5.47	7.01	13.7	7.09	12.76	13.78
250	10	5.47	7.01	14.69	8.07	15.75	17.72
300	12	5.47	7.01	15.67	9.06	18.11	19.69


1) Depending on the cable entry used: values up to +1.18 in

2) Reference values: depending on the pressure rating, design and order option

3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

Order code for "Housing", option M "Compact, polycarbonate"

Sensor with aluminum half-shell housing



A0042708

DN		A ¹⁾	B	Order code for "Design"			L ³⁾
				Options D, E, H, I			
[mm]	[in]	[in]	[in]	C ²⁾	D ²⁾	E ²⁾	[in]
25	1	5.2	6.77	10.04	3.31	4.72	7.87
32	-	5.2	6.77	10.04	3.31	4.72	7.87
40	1 ½	5.2	6.77	10.04	3.31	4.72	7.87
50	2	5.2	6.77	10.04	3.31	4.72	7.87
65	-	5.2	6.77	11.02	4.29	7.09	7.87
80	3	5.2	6.77	11.02	4.29	7.09	7.87
100	4	5.2	6.77	11.02	4.29	7.09	9.84
125	-	5.2	6.77	12.6	5.91	10.24	9.84
150	6	5.2	6.77	12.6	5.91	10.24	11.81
200	8	5.2	6.77	13.58	7.09	12.76	13.78
250	10	5.2	6.77	14.57	8.07	15.75	17.72
300	12	5.2	6.77	15.55	9.06	18.11	19.69


1) Depending on the cable entry used: values up to +1.18 in

2) Reference values: depending on the pressure rating, design and order option

3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

DN 350 to 900 (14 to 36")

Order code for "Housing", option A "Compact, aluminum, coated"




A0042708

DN		A ¹⁾	B	Order code for "Design"						L ³⁾	
				Options E, F			Option G				
[mm]	[in]	[in]	[in]	C ²⁾	D ²⁾	E ²⁾	C ²⁾	D ²⁾	E ²⁾	[in]	
350	14	5.47	7.01	17.99	9.65	19.29	-	-	-	21.65	
375	15	5.47	7.01	19.02	10.67	21.34	-	-	-	23.62	
400	16	5.47	7.01	19.02	10.67	21.34	-	-	-	23.62	
450	18	5.47	7.01	18.31	11.77	23.54	20	13.11	26.22	23.62 ⁴⁾	25.59 ⁵⁾
500	20	5.47	7.01	19.29	12.76	25.51	21.02	14.13	28.23	23.62	25.59
600	24	5.47	7.01	21.26	14.37	28.74	23.07	16.18	32.32	23.62	30.71
700	28	5.47	7.01	23.66	16.93	33.86	27.09	20.16	40.31	27.56	35.83
750	30	5.47	7.01	25.16	18.39	36.77	27.09	20.16	40.31	29.53	38.39
800	32	5.47	7.01	25.91	19.13	38.27	27.91	21.02	41.93	31.5	40.94
900	36	5.47	7.01	27.87	21.1	42.2	30.94	24.02	47.95	35.43	46.06

- 1) Depending on the cable entry used: values up to +1.18 in
- 2) Reference values: depending on the pressure rating, design and order option
- 3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 4) Order code for "Design", option F "Fixed flange, short installed length"
- 5) Order code for "Design", option G "Fixed flange, long installed length"

Order code for "Housing", option M "Compact, polycarbonate"




A0042708

DN		A ¹⁾	B	Order code for "Design"						L ³⁾	
				Options E, F			Option G				
[mm]	[in]	[in]	[in]	C ²⁾	D ²⁾	E ²⁾	C ²⁾	D ²⁾	E ²⁾	[in]	[in]
350	14	5.2	6.77	17.87	9.65	19.29	-	-	-	21.65	
375	15	5.2	6.77	18.9	10.67	21.34	-	-	-	23.62	
400	16	5.2	6.77	18.9	10.67	21.34	-	-	-	23.62	
450	18	5.2	6.77	18.19	11.77	23.54	19.88	13.11	26.22	23.62 ⁴⁾	25.59 ⁵⁾
500	20	5.2	6.77	19.17	12.76	25.51	20.91	14.13	28.23	23.62	25.59
600	24	5.2	6.77	21.14	14.37	28.74	22.95	16.18	32.32	23.62	30.71
700	28	5.2	6.77	23.54	16.93	33.86	26.97	20.16	40.31	27.56	35.83
750	30	5.2	6.77	25.04	18.39	36.77	26.97	20.16	40.31	29.53	38.39
800	32	5.2	6.77	25.79	19.13	38.27	27.8	21.02	41.93	31.5	40.94
900	36	5.2	6.77	27.76	21.1	42.2	30.83	24.02	47.95	35.43	46.06

- 1) Depending on the cable entry used: values up to +1.18 in
- 2) Reference values: depending on the pressure rating, design and order option
- 3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 4) Order code for "Design", option F "Fixed flange, short installed length"
- 5) Order code for "Design", option G "Fixed flange, long installed length"

DN 1000 to 3000 (40 to 120")

Order code for "Housing", option A "Compact, aluminum, coated"



A0042708

DN		A ¹⁾	B	C ²⁾	D ²⁾	E ²⁾	L ³⁾	
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	
1000	40	5.47	7.01	29.88	22.91	45.83	39.37 ⁴⁾	51.18 ⁵⁾
-	42	5.47	7.01	31.3	24.33	48.66	41.34	53.74
1200	48	5.47	7.01	34.37	27.4	54.8	47.24	61.42
-	54	5.47	7.01	38.82	31.85	63.66	53.15	69.09
1400	-	5.47	7.01	38.82	31.85	63.66	55.12	71.65
-	60	5.47	7.01	42.76	35.79	71.54	59.06	76.77
1600	-	5.47	7.01	42.76	35.79	71.54	62.99	81.89
-	66	5.47	7.01	44.76	37.8	75.55	64.96	84.45
1800	72	5.47	7.01	46.97	40	80	70.87	92.13
-	78	5.47	7.01	51.38	44.37	88.74	78.74	102.36
2000	-	5.47	7.01	51.38	44.37	88.74	78.74	102.36
-	84	5.47	7.01	55.31	48.31	96.61	84.65	
2200	-	5.47	7.01	55.31	48.31	96.61	86.61	
-	90	5.47	7.01	59.45	48.31	104.88	90.55	
2400	-	5.47	7.01	59.45	52.44	104.88	94.49	
-	96	5.47	7.01	63.35	56.34	112.64	96.46	
-	102	5.47	7.01	66.69	59.69	119.37	102.36	
2600	-	5.47	7.01	63.78	56.77	113.50	102.36	
-	108	5.47	7.01	70.12	63.07	126.14	108.27	
2800	-	5.47	7.01	67.91	60.91	121.77	110.24	
-	114	5.47	7.01	73.46	66.46	132.87	114.17	
3000	-	5.47	7.01	71.85	64.84	129.65	118.11	
-	120	5.47	7.01	76.85	69.84	139.65	120.08	

1) Depending on the cable entry used: values up to +1.18 in


2) Reference values: depending on the pressure rating, design and order option

3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

4) Order code for "Design", option F "Fixed flange, short installed length"

5) Order code for "Design", option G "Fixed flange, long installed length"

Order code for "Housing", option M "Compact, polycarbonate"




A0042708

DN		A ¹⁾	B	C ²⁾	D	E	L ³⁾	
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	
1000	40	5.2	6.77	29.76	22.91	45.83	39.37 ⁴⁾	51.18 ⁵⁾
-	42	5.2	6.77	31.18	24.33	48.66	41.34	53.74
1200	48	5.2	6.77	34.25	27.4	54.8	47.24	61.42
-	54	5.2	6.77	38.7	31.85	63.66	53.15	69.09
1400	-	5.2	6.77	38.7	31.85	63.66	55.12	71.65
-	60	5.2	6.77	42.64	35.79	71.54	59.06	76.77
1600	-	5.2	6.77	42.64	35.79	71.54	62.99	81.89
-	66	5.2	6.77	44.65	37.8	75.55	64.96	84.45
1800	72	5.2	6.77	46.85	40	80	70.87	92.13
-	78	5.2	6.77	51.26	44.37	88.74	78.74	102.36
2000	-	5.2	6.77	51.26	44.37	88.74	78.74	102.36
-	84	5.2	6.77	55.2	48.31	96.61	84.65	
2200	-	5.2	6.77	55.2	48.31	96.61	86.61	
-	90	5.2	6.77	59.33	48.31	104.88	90.55	
2400	-	5.2	6.77	59.33	52.44	104.88	94.49	
-	96	5.47	7.01	63.47	56.34	112.64	96.46	
-	102	5.47	7.01	66.81	59.69	119.37	102.36	
2600	-	5.47	7.01	63.9	56.77	113.50	102.36	
-	108	5.47	7.01	70.24	63.07	126.14	108.27	
2800	-	5.47	7.01	68.03	60.91	121.77	110.24	
-	114	5.47	7.01	73.58	66.46	132.87	114.17	
3000	-	5.47	7.01	71.97	64.84	129.65	118.11	
-	120	5.47	7.01	76.97	69.84	139.65	120.08	

- 1) Depending on the cable entry used: values up to +1.18 in
- 2) Reference values: depending on the pressure rating, design and order option
- 3) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 4) Order code for "Design", option F "Fixed flange, short installed length"
- 5) Order code for "Design", option G "Fixed flange, long installed length"

Remote version

Transmitter remote version




A0042715

Order code for "Housing"	A ¹⁾ [in]	B [in]	C [in]	D [in]	E [in]
Option N "Remote, polycarbonate"	5.2	7.36	6.77	12.09	5.12
Option P and T "Remote, coated aluminum"	5.47	7.28	7.01	12.17	5.12

1) Depending on the cable entry used: values up to +1.18 in

Sensor connection housing



A0042716


Housing material	A ¹⁾ [in]	B [in]
Polycarbonate plastic ²⁾	4.45	4.41
Aluminum, coated ³⁾	5.83	5.35

- 1) Depending on the cable entry used: values up to + 1.18 in
- 2) In conjunction with order code for "Sensor option", options CB, CC, CD, CE
- 3) In conjunction with order code for "Sensor option", options CF, CQ, C3

DN 25 to 300 (1 to 12") aluminum half-shell housing

Sensor with aluminum half-shell housing.

Sensor connection housing: aluminum, AlSi10Mg, coated




DN		Order code for "Design"			
		Options D, E, H, I			
[mm]	[in]	C ¹⁾ [in]	D [in]	E [in]	L ²⁾ [in]
25	1	7.76	3.31	4.72	7.87
32	-	7.76	3.31	4.72	7.87
40	1 ½	7.76	3.31	4.72	7.87
50	2	7.76	3.31	4.72	7.87
65	-	8.74	4.29	7.09	7.87
80	3	8.74	4.29	7.09	7.87
100	4	8.74	4.29	7.09	9.84
125	-	10.31	5.91	10.24	9.84
150	6	10.31	5.91	10.24	11.81
200	8	11.3	7.09	12.76	13.78
250	10	12.28	8.07	15.75	17.72
300	12	13.27	9.06	18.11	19.69

- 1) Reference values: depending on the pressure rating, design and order option
- 2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

DN 25 to 300 (1 to 12") fully welded housing

Sensor with fully welded carbon steel housing:
Order code for "Sensor option", options CB, CC, CD, CE




A0041519

DN		Order code for "Design"			
		Options A, E			
[mm]	[in]	C ¹⁾ [in]	D ¹⁾ [in]	E ¹⁾ [in]	L ²⁾ [in]
25	1	7.44	2.76	5.51	7.87
32	-	7.44	2.76	5.51	7.87
40	1 ½	7.44	2.76	5.51	7.87
50	2	7.44	2.76	5.51	7.87
65	-	7.95	3.23	6.5	7.87
80	3	8.15	3.43	6.89	7.87
100	4	8.62	3.94	7.87	9.84
125	-	9.13	4.45	8.9	9.84
150	6	10	5.28	10.59	11.81
200	8	10.98	6.3	12.6	13.78
250	10	12.32	7.6	15.24	17.72
300	12	13.31	8.58	17.2	19.69

1) Reference values: depending on the pressure rating, design and order option

2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

DN 350 to 900 (14 to 36")




A0041519

DN		Order code for "Design"							L ²⁾ [in]	
		Options E, F			Option G					
[mm]	[in]	C ¹⁾ [in]	D [in]	E [in]	C [in]	D [in]	E [in]			
350	14	15.55	9.65	19.29	-	-	-	21.65		
375	15	16.57	10.67	21.34	-	-	-	23.62		
400	16	16.57	10.67	21.34	-	-	-	23.62		
450	18	15.87	11.77	23.54	17.56	13.11	26.22	23.62 ³⁾	25.59 ⁴⁾	
500	20	16.85	12.76	25.51	18.58	14.13	28.23	23.62	25.59	
600	24	18.82	14.37	28.74	20.63	16.18	32.32	23.62	30.71	
700	28	21.22	16.93	33.86	24.65	20.16	40.31	27.56	35.83	
750	30	22.72	18.39	36.77	24.65	20.16	40.31	29.53	38.39	
800	32	23.46	19.13	38.27	25.47	21.02	41.93	31.5	40.94	
900	36	25.43	21.1	42.2	28.5	24.02	47.95	35.43	46.06	

- 1) Reference values: depending on the pressure rating, design and order option
- 2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).
- 3) Order code for "Design", option F "Fixed flange, short installed length"
- 4) Order code for "Design", option G "Fixed flange, long installed length"

DN 1000 to 3000 (40 to 120")



A0041519

DN		C ¹⁾	D ¹⁾	E ¹⁾	L ²⁾	
[mm]	[in]	[in]	[in]	[in]	[in]	
1000	40	27.48	22.91	45.83	39.37 ³⁾	51.18 ⁴⁾
-	42	28.9	24.33	48.66	41.34	53.74
1200	48	31.97	27.4	54.8	47.24	61.42
-	54	36.42	31.85	63.66	53.15	69.09
1400	-	36.42	31.85	63.66	55.12	71.65
-	60	40.35	35.79	71.54	59.06	76.77
1600	-	40.35	35.79	71.54	62.99	81.89
-	66	42.36	37.8	75.55	64.96	84.45
1800	72	44.57	40	80	70.87	92.13
-	78	48.98	44.37	88.74	78.74	102.36
2000	-	48.98	44.37	88.74	78.74	102.36
-	84	52.91	48.31	96.61	84.65	
2200	-	52.91	48.31	96.61	86.61	
-	90	57.05	48.31	104.88	90.55	
2400	-	57.05	52.44	104.88	94.49	
-	96	60.95	56.34	112.64	96.46	
-	102	64.29	59.69	119.37	102.36	
2600	-	61.38	56.77	113.50	102.36	
-	108	67.72	63.07	126.14	108.27	
2800	-	65.51	60.91	121.77	110.24	
-	114	71.06	66.46	132.87	114.17	
3000	-	69.45	64.84	129.65	118.11	
-	120	74.45	69.84	139.65	120.08	

1) Reference values: depending on the pressure rating, design and order option

2) Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water).

3) Order code for "Design", option F "Fixed flange, short installed length"

4) Order code for "Design", option G "Fixed flange, long installed length"


Fixed flange

Flange similar to ASME B16.5, Class 150

- Carbon steel: order code for "Process connection", option A1K
- Stainless steel: order code for "Process connection", option A1S

Surface roughness: Ra 250 to 492 µin

E: Internal diameter depends on the liner → *Measuring tube specification in US units*, 70




DN [in]	A [in]	B [in]	C [in]	D [in]
1	4.25	3.12	4 × Ø0.63	0.5
1 ½	5	3.88	4 × Ø0.63	0.63
2	6	4.75	4 × Ø0.75	0.69
3	7.5	6	4 × Ø0.75	0.88
4	9	7.5	8 × Ø0.75	0.88
6	11	9.5	8 × Ø0.88	0.94
8	13.5	11.75	8 × Ø0.88	1.06
10	16	14.25	12 × Ø1	1.17
12	19	17	12 × Ø1	1.19
14	21.06	18.75	12 × Ø1.13	1.39
16	23.43	21.25	16 × Ø1.13	1.46
18	25	22.75	16 × Ø1.25	1.58
20	27.56	25	20 × Ø1.25	1.7
24	32.09	29.5	20 × Ø1.37	1.89

Flange similar to ASME B16.5, Class 300

- Carbon steel: order code for "Process connection", option A2K
- Stainless steel: order code for "Process connection", option A2S

Surface roughness: Ra 250 to 492 µin

E: Internal diameter depends on the liner → *Measuring tube specification in US units*, 70




DN [in]	A [in]	B [in]	C [in]	D [in]
1	4.88	3.5	4 × Ø0.75	0.63
1 ½	6.12	4.5	4 × Ø0.88	0.75
2	6.5	5	8 × Ø0.75	0.82
3	8.25	6.62	8 × Ø0.88	1.06
4	10	7.88	8 × Ø0.88	1.19
6	12.5	10.62	12 × Ø0.88	1.38

Flange similar to AWWA, Cl. D

Order code for "Process connection", option W1K

Surface roughness: Ra 250 to 492 µin

E: Internal diameter depends on the liner → *Measuring tube specification in US units*, 70

A0041915

DN [in]	A [in]	B [in]	C [in]	D [in]
28	36.5	34	28 × Ø1.38	1.31
30	38.74	36	28 × Ø1.38	1.38
32	41.73	38.5	28 × Ø1.65	1.5
36	45.98	42.75	32 × Ø1.65	1.63
40	50.75	47.25	36 × Ø1.65	1.63
42	52.99	49.5	36 × Ø1.65	1.75
48	59.49	56	44 × Ø1.65	1.88
54	66.26	62.75	44 × Ø1.89	2.13
60	73.03	69.25	52 × Ø1.89	2.25
66	80	76	52 × Ø1.89	2.5
72	86.5	82.5	60 × Ø1.89	2.63
78	92.99	89	64 × Ø2.13	2.75
84	99.8	95.5	64 × Ø2.13	2.88
90	106.5	107	68 × Ø2.36	3
96	113.27	108.50	68 × Ø2.37	3.25
102	120.00	114.50	68 × Ø2.63	3.25
108	126.73	120.75	68 × Ø2.63	3.38
114	133.50	126.75	68 × Ø2.87	3.50
120	140.24	132.75	68 × Ø2.87	3.50


Lap joint flange

Lap joint flange similar to ASME B16.5, Class 150

- **Carbon steel:** order code for "Process connection", option A12
- **Stainless steel:** order code for "Process connection", option A14

Surface roughness (flange): Ra 248 to 492 µin

F: Internal diameter depends on the liner → *Measuring tube specification in US units*, 70




A0042254

DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]
1	4.33	3.15	4 × Ø0.63	0.55	1.93
1 ½	4.92	3.86	4 × Ø0.63	0.69	2.8
2	5.91	4.76	4 × Ø0.75	0.75	3.46
3	7.48	5.98	4 × Ø0.75	0.94	4.72
4	9.06	7.48	8 × Ø0.75	0.94	5.83
6	11.02	9.49	8 × Ø0.91	0.98	8.23
8	13.58	11.73	8 × Ø0.91	1.14	10.39
10	15.94	14.25	12 × Ø0.98	1.18	12.48
12	19.09	17.01	12 × Ø0.98	1.26	14.88

Accessories

Weather protection cover



A0042332


A [in]	B [in]	D [in]	E [in]	F [in]
10.12	0.47	11.02	5.51	5.51

Ground disks for flanges


DN 15 to 300 (½ to 12")		DN	Pressure rating	A	B	C ¹⁾	D	E	F
		[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
	25	1"	2)	3.44	0.26	0.08	1.02	2.44	3.05
	32	1 ¼"	2)	3.72	0.26	0.08	1.38	3.15	3.44
	40	1 ½"	2)	4.06	0.26	0.08	1.61	3.23	3.98
	50	2"	2)	4.25	0.26	0.08	2.05	3.98	4.55
	65	2 ½"	2)	4.65	0.26	0.08	2.68	4.76	5.18
	80	3"	2)	5.31	0.26	0.08	3.15	5.16	6.08
	100	4"	2)	6.02	0.26	0.08	4.09	6.14	7.34
	125	5"	2)	6.3	0.26	0.08	5.12	7.36	8.13
	150	6"	2)	7.24	0.26	0.08	6.22	8.54	10.08
	200	8"	2)	8.07	0.26	0.08	8.11	10.51	11.34
	250	10"	2)	9.45	0.26	0.08	10.24	12.91	14.13
	300	12"	PN 10 PN 16 Cl. 150		10.75	0.26	0.08	12.28	14.76

A0042332

- 1) Material thickness
- 2) In the case of DN 1 to 10", ground disks can be used for all the flange standards/pressure ratings which can be supplied in the standard version.

DN 300 to 600 (12 to 24")		DN	Rating	A	B	C ¹⁾	D	E	F
		[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
 <p>A0042323</p>		300	PN 25 JIS 10K JIS 20K	10.55	0.35	0.08	12.2	14.76	15.91
		350	PN 6 PN 10 PN 16	14.37	0.35	0.08	13.5	16.54	18.86
		375	PN 16	15.55	0.35	0.08	15.47	18.15	20.59
		400	PN 6 PN 10 PN 16	15.55	0.35	0.08	15.47	18.5	21.34
		450	PN 6 PN 10 PN 16	16.42	0.35	0.08	17.28	20.67	22.95
		500	PN 6 PN 10 PN 16	18.11	0.35	0.08	19.41	22.64	25.59
		600	PN 6 PN 10 PN 16	20.55	0.35	0.08	23.35	26.61	30.16

1) Material thickness

DN 700 to 1200 (28 to 48")		DN	Pressure rating	A	B	C ¹⁾	D	E
		[mm]	[in]	[in]	[in]	[in]	[in]	[in]
 <p>A0042324</p>		700	PN 6 PN10 PN16 Cl, D	18.11 18.9 19.29 19.45	0.25	0.08	27.44 27.28 27.05 27.28	30.94 32.01 31.77 32.76
		750	Cl, D	20.59	0.25	0.08	29.25	34.76
		800	PN 6 PN 10 PN 16 Cl, D	20.47 21.26 21.65 22.09	0.25	0.08	31.46 31.3 31.06 31.3	35.16 36.22 35.98 37.01
		900	PN 6 PN 10 PN 16 Cl, D	22.44 23.23 23.43 24.21	0.25	0.08	35.31 35.16 34.88 35.16	39.09 40.16 39.92 41.26
		1000	PN 6 PN 10 PN 16 Cl, D	24.41 25.59 25.98 26.57	0.25	0.08	39.33 39.17 38.9 39.17	43.03 44.37 44.53 45.79
		-	Cl, D	27.72	0.25	0.08	41.1	48.03
		1200	PN 6 PN 10 PN 16 Cl, D	28.86 29.92 30.51 30.94	0.25	0.08	47.36 47.09 46.77 47.09	51.57 52.91 52.95 54.53

1) Material thickness

Local display

Operation concept	124
Operation options	125
Operating tools	125

Operation concept

Operation method	Operation via local display with touchscreen ¹⁾ Operation via: <ul style="list-style-type: none"> ▪ SmartBlue app ²⁾ ▪ Commubox FXA291
Reliable operation	<ul style="list-style-type: none"> ▪ Operation in local language ▪ Uniform operating philosophy in device and in the SmartBlue App ▪ Write protection ▪ When electronics modules are replaced: configurations are transferred using the T-DAT Backup device memory. The device memory contains process data, device data and the event logbook. No reconfiguration is necessary.
Diagnostic behavior	Efficient diagnostic behavior increases measurement availability: <ul style="list-style-type: none"> ▪ Open remedial actions via local display and SmartBlue app ▪ Diverse simulation options ▪ Logbook of events that have occurred

1) Only for HART and Modbus RS485 communication protocols

2) Optional via order code "Display; operation", options H, J or K

IO-Link



The device-specific parameters are configured via IO-Link. There are specific configuration or operating programs from different manufacturers available to the user for this purpose. The device description file (IODD) is provided for the device.

IO-Link operating concept

Operator-oriented menu structure for user-specific tasks. Efficient diagnostic behavior increases measurement availability:

- Diagnostic messages
- Remedial action
- Simulation options

IODD download

Two options to download the IODD :

- www.endress.com/download
- <https://ioddfinder.io-link.com/>

www.endress.com/download

1. Select "Device Drivers".
2. Select the "IO Device Description (IODD)" entry under "Type".
3. Select "Product root".
4. Click "Search".

↳ A list of search results is displayed.

Select the appropriate version and download.

<https://ioddfinder.io-link.com/>

1. Enter "Endress" as the manufacturer and select.
 2. Select product name.
- ↳ A list of search results is displayed.

Select the appropriate version and download.



For detailed IO-Link information, see "IO-Link" Special Documentation for the device
→ *Related documentation*, 6

Operation options

Local display

11 Only for HART and Modbus RS485 communication protocols

Display elements:

- LCD touch screen ¹⁾
- Depends on the orientation, automatic alignment of the local display
- Configuration of display format for measured variables and status variables

Operating elements:

- Touch screen ¹⁾
- Local display can also be accessed in the hazardous area

SmartBlue app

- The SmartBlue app allows the user to put devices into operation and operate them.
- Based on Bluetooth
- No separate driver required
- Available for mobile handheld terminals, tablets and smartphones
- Suitable for convenient and secure access to devices in hard-to-reach locations or in hazardous areas
- Can be used within a 20 m (65.6 ft) radius of the device
- Encrypted and secure data transmission
- No data loss during commissioning and maintenance
- Diagnostic information and process information in real time

1) Only for HART and Modbus RS485 communication protocols

Operating tools

Operating tools	Operating unit	Interface	Additional information
DeviceCare SFE100	<ul style="list-style-type: none"> ▪ Notebook ▪ PC ▪ Tablet with Microsoft Windows system 	<ul style="list-style-type: none"> ▪ CDI service interface ▪ Fieldbus protocol 	Innovation brochure IN01047S
FieldCare SFE500	<ul style="list-style-type: none"> ▪ Notebook ▪ PC ▪ Tablet with Microsoft Windows system 	<ul style="list-style-type: none"> ▪ CDI service interface ▪ Fieldbus protocol 	Operating Instructions BA00027S and BA00059S
SmartBlue app	<ul style="list-style-type: none"> ▪ Devices with iOS: iOS9.0 or higher ▪ Devices with Android: Android 4.4 KitKat or higher 	Bluetooth	Endress+Hauser SmartBlue App: <ul style="list-style-type: none"> ▪ Google Playstore (Android) ▪ iTunes Apple Shop (iOS devices)
Device Xpert	Field Xpert SFX 100/350/370	HART fieldbus protocol	Operating Instructions BA01202S

Certificates and approvals

Non-Ex approval	128
Pressure Equipment Directive	128
Drinking water approval	128
Pharmaceutical compatibility	128
HART certification	128
Radio approval	128
Additional approvals	128
Additional certification	128
External standards and guidelines	128

Non-Ex approval

- cSAus
- EAC
- UKCA

Pressure Equipment Directive

- CRN
- PED Cat. II/III
- PESR Cat. II/III

Drinking water approval

- ACS
- KTW/W270
- NSF 61
- WRAS BS 6920

Pharmaceutical compatibility

- FDA
- USP Class VI
- TSE/BSE Certificate of Suitability

HART certification

The device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability).

Radio approval

The device has radio approvals.

Additional approvals

VDS (for stationary fire extinguishing systems)

Additional certification

- IO-Link
Self-certification with Manufacturer Declaration
- CRN approval
Some device versions have a CRN approval. A CRN-approved process connection with a CSA approval must be ordered for a CRN-approved device.
- EN10204-3.1 material certificate, wetted parts and sensor housing (order code for "Test, certificate", option JA)
- Pressure test, internal process, test report (order code for "Test, certificate", option JB)
- Surface roughness test ISO4287/Ra, (wetted parts), test report (option JE)
- Compliance with requirements derived from cGMP, Declaration (option JG)

External standards and guidelines

- IEC/EN 60529
Degrees of protection provided by enclosure (IP code)
- IEC/EN 60068-2-6
Environmental influences: Test procedure - Test Fc: vibration (sinusoidal)
- IEC/EN 60068-2-31
Environmental influences: Test procedure - Test Ec: shocks due to rough handling, primarily for devices.

- IEC/EN 61010-1
Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements.
- GB 30439.5
Safety requirements for industrial automation products - Part 5: Flowmeter safety requirements
- CAN/CSA-C22.2 No. 61010-1-12
Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1 General Requirements.
- IEC 61131-9
Interface for communication with small sensors and actuators via a point-to-point connection
- IEC/EN 61326
Emission in accordance with Class A requirements; Electromagnetic compatibility (EMC requirements)
- ANSI/ISA-61010-1 (82.02.01)
Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1 General Requirements.
- NAMUR NE 21
Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment.
- NAMUR NE 32
Data retention in the event of a power failure in field and control instruments with microprocessors.
- NAMUR NE 43
Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.
- NAMUR NE 53
Software of field devices and signal-processing devices with digital electronics.
- NAMUR NE 105
Specifications for integrating fieldbus devices in engineering tools for field devices.
- NAMUR NE 107
Self-monitoring and diagnosis of field devices.
- NAMUR NE 131
Requirements for field devices for standard applications.
- ETSI EN 300 328
Guidelines for 2.4 GHz radio components
- EN 301489
Electromagnetic compatibility and radio spectrum matters (ERM).



Application packages

Use	132
Heartbeat Verification + Monitoring	132

Use

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the relevant order code is available from your local Endress+Hauser sales organization or on the product page of the Endress+Hauser website: www.endress.com.

Heartbeat Verification + Monitoring

Heartbeat Verification

Availability depends on the product structure.

Meets the requirement for traceable verification according to DIN ISO 9001:2015 Clause 7.6 a) "Control of monitoring and measuring equipment":

- Functional testing in the installed state without interrupting the process.
- Traceable verification results on request, including report.
- Simple testing process with local operation or other operating interfaces.
- Clear measuring point assessment (pass/fail) with high total test coverage within the framework of manufacturer specifications.
- Extension of calibration intervals according to operator's risk evaluation.

Heartbeat Monitoring

Availability depends on the product structure.

Heartbeat Monitoring continuously provides data characteristic of the measuring principle to an external condition monitoring system, facilitating preventive maintenance or process analysis. This data enables the operator to:




- Draw conclusions - using this data and other information - about the measuring performance over time.
- Schedule servicing in time.
- Monitor the process quality or product quality .

Accessories


Device-specific accessories	134
Communication-specific accessories	135
Service-specific accessory	136
System components	136

Device-specific accessories









Transmitter

Accessories	Description	Order number
Proline 10 transmitter	 Installation Instructions EA01350D	5XBBXX-*...*
Weather protection cover	Protects the device from weather exposure:  Installation Instructions EA01351D	71502730
Connecting cable	Can be ordered with the device. The following cable lengths are available: order code for "Cable, sensor connection" <ul style="list-style-type: none"> ▪ 5 m (16 ft) ▪ 10 m (32 ft) ▪ 20 m (65 ft) ▪ User-configurable cable length m (ft)  Max. cable length: 200 m (660 ft)	DK5013-*...*
Ground cable	1 ground cable set for potential equalization, consisting of 2 ground cables	



Sensor

Accessories	Description
Ground disks	Ground medium in lined measuring pipes.  Installation Instructions EA00070D



Communication-specific accessories

Accessory	Description
Commubox FXA195 USB/HART modem	Intrinsically safe HART communication with FieldCare and FieldXpert  Technical Information TI00404F
Commubox FXA291	Connects the Endress+Hauser devices with the CDI interface (= Endress+Hauser Common Data Interface) to the USB interface of a personal computer or laptop.  Technical Information TI405C/07
Commubox FXA291	Connects the Endress+Hauser devices with the CDI interface (= Endress+Hauser Common Data Interface) to the USB interface of a personal computer or laptop.  Technical Information TI405C/07
HART loop converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.  <ul style="list-style-type: none"> ▪ Technical Information TI00429F ▪ Operating Instructions BA00371F
Fieldgate FXA42	Transmission of measured values from connected 4 to 20 mA analog and digital devices.  <ul style="list-style-type: none"> ▪ Technical Information TI01297S ▪ Operating Instructions BA01778S ▪ Product page: www.endress.com/fxa42
Field Xpert SMT50	The Field Xpert SMT50 table PC for device configuration enables mobile plant asset management. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.  <ul style="list-style-type: none"> ▪ Technical Information TI01555S ▪ Operating Instructions BA02053S ▪ Product page: www.endress.com/smt50
Field Xpert SMT70	Tablet PC for the configuration of the device. Enables mobile Plant Asset Management to manage the devices with a digital communication interface. Suitable for Zone 2.  <ul style="list-style-type: none"> ▪ Technical Information TI01342S ▪ Operating Instructions BA01709S ▪ Product page: www.endress.com/smt70
Field Xpert SMT77	Tablet PC for the configuration of the device. Enables mobile Plant Asset Management to manage the devices with a digital communication interface. Suitable for Zone 1.  <ul style="list-style-type: none"> ▪ Technical Information TI01418S ▪ Operating Instructions BA01923S ▪ Product page: www.endress.com/smt77
FieldPort SFP20	The FieldPort SFP20 is a USB interface for the configuration of Endress+Hauser IO-Link devices, and also of devices from other vendors. Combined with the IO-Link CommDTM (DeviceCare, FieldCare, Field Xpert) and the IODD Interpreter, the FieldPort complies with the FDT/DTM standards.
IO-Link master BL20	IO-Link master from Turck for DIN rails supports PROFINET, EtherNet/IP and Modbus TCP. With web server for easy configuration.

Service-specific accessory

Accessory	Description	Order code
Applicator	Software for selecting and sizing Endress+Hauser devices.	https://portal.endress.com/webapp/applicator
Netilion	<p>IIoT ecosystem: Unlock knowledge</p> <p>With the Netilion IIoT ecosystem, Endress+Hauser allows you to optimize your plant performance, digitize workflows, share knowledge, and enhance collaboration.</p> <p>Based on decades of experience in process automation, Endress+Hauser offers the process industry an IIoT ecosystem that enables you to gain useful insights from data. These insights can be used to optimize processes, leading to increased plant availability, efficiency, and reliability - ultimately resulting in a more profitable plant.</p>	www.netilion.endress.com
FieldCare	<p>FDT-based plant asset management software from Endress+Hauser. Management and configuration of Endress+Hauser devices.</p> <p> Operating Instructions BA00027S and BA00059S</p>	<ul style="list-style-type: none"> ▪ Device driver: www.endress.com → Download Area ▪ CD-ROM (contact Endress+Hauser) ▪ DVD (contact Endress+Hauser)
DeviceCare	<p>Software for connecting and configuring Endress+Hauser devices.</p> <p> <ul style="list-style-type: none"> ▪ Technical Information: TI01134S ▪ Innovation brochure: IN01047S </p>	<ul style="list-style-type: none"> ▪ Device driver: www.endress.com → Download Area ▪ CD-ROM (contact Endress+Hauser) ▪ DVD (contact Endress+Hauser)

System components

Accessories	Description
Memograph M	<p>Graphic data manager:</p> <ul style="list-style-type: none"> ▪ Record measured values ▪ Monitor limit values ▪ Analyze measuring points <p> <ul style="list-style-type: none"> ▪ Technical Information TI00133R ▪ Operating Instructions BA00247R </p>
iTEMP	<p>Temperature transmitter:</p> <ul style="list-style-type: none"> ▪ Measure the absolute pressure and gauge pressure of gases, vapors and liquids ▪ Read the medium temperature <p> "Fields of Activity" document FA00006T</p>



71758368

www.addresses.endress.com
