

Safety Instructions

Proline Promass 500

ATEX: II3G (Zone 2)

IECEX: EPL Gc (Zone 2)



BG - Правила за техниката на безопасност за електрически средства за производство във взривоопасни зони. Ако не разбирате езика на това ръководство има възможност да спорячате при нас едно ръководство, преведено на езика на Вашата страна.

ЕС декларация за съответствие

Производителят Endress+Hauser декларира с това заявление за съответствие и с предявяването на сертификата CE, че този продукт отговаря на изискванията на съответните европейски директиви. Прилаганите директиви, норми и документи са указани в заявлението за съответствие.

CS - Bezpečnostní pokyny pro elektrické přístroje v místech s nebezpečím výbuchu. Pokud nemáte možnost přečíst si tento návod, můžete si u nás objednat návod přeložený do svého jazyka.

EU prohlášení o shodě

Společnost Endress+Hauser prohlašuje prostřednictvím tohoto prohlášení a použitím značky CE, že tento výrobek vyhovuje příslušným evropským směrnicím. Zmíněné směrnice, normy a dokumenty jsou uvedeny v Prohlášení o shodě.

DA - Sikkerhedsforskrifter for elektriske apparater certificeret til brug i eksplosionsfarlige områder. Hvis du ikke forstår denne manual, kan en oversat kopi af den på dit eget sprog bestilles fra os.

EU-overensstemmelseserklæring

Med denne overensstemmelseserklæring og tilføjelsen af CE-mærket sikrer producenten Endress+Hauser, at produktet er i overensstemmelse med relevante europæiske direktiver. Dokumentation for overensstemmelsen gives i de anførte direktiver, standarder og dokumenter.

EL - Οδηγίες ασφαλείας ηλεκτρικών συσκευών για επικίνδυνες για έκρηξη περιοχές. Σε περίπτωση που δεν μπορείτε να διαβάσετε αυτές τις οδηγίες, τότε μπορείτε να παραγγείλετε ένα αντίτυπο μεταφρασμένο στη γλώσσα σας.

Δήλωση συμμόρφωσης ΕΕ

Με αυτή τη δήλωση πιστότητας και την τοποθέτηση του σήματος CE ο κατασκευαστής Endress+Hauser δηλώνει, ότι αυτό το προϊόν συμμορφώνεται με τις ευρωπαϊκές οδηγίες που πρέπει να εφαρμοστούν. Οι οδηγίες, τα πρότυπα και τα έγγραφα που εφαρμόστηκαν αναφέρονται στη δήλωση πιστότητας.

ES - Instrucciones de seguridad de aparatos eléctricos homologados para su utilización en áreas expuestas a riesgos de deflagración. Si no entiende este manual, puede pedir un ejemplar en su idioma.

Declaración UE de conformidad

Por la presente declaración y la inclusión de la marca CE, el fabricante Endress+Hauser, declara que el producto cumple con las directivas europeas pertinentes. Las directivas, normas y documentos de aplicación se indican en la declaración de conformidad.

ET - Ohutusjuhised plahvatusohtlikus keskkonnas kasutatavate elektriseadmete kohta. Kui Te ei saa käesolevast juhendist aru, võite meilt tellida Teie riigikeelde tõlgitud juhendi.

EL i vastavusdeklaratsioon

Tootja Endress+Hauser kinnitab juurdelisatud vastavusdeklaratsiooni esitamisega ja CE-märgise kandmisega tootele, et käesolev toode vastab kohaldatavate Euroopa Liidu direktiivide nõuetele. Kohaldatavad direktiivid, standardid ja dokumendid on ära toodud vastavusdeklaratsioonis.

FI - Turvallisuusohjeita sähkölaitteille, jotka on vahvistettu käytettäväksi räjähdysvaarallisilla alueilla. Jos et ymmärrä tätä käsikirjaa, voit tilata meiltä käännöksen omalla kansallisella kielelläsi.

EU-vaatimustenmukaisuusvakuutus

Valmistaja Endress+Hauser vakuuttaa täällä vaatimustenmukaisuustodistuksella ja CE-merkin kiinnittämisellä, että tämä tuote täyttää sovellettavien EU-direktiivien määräykset. Sovellettavat direktiivit, normit ja dokumentit on merkitty vaatimustenmukaisuustodistukseen.

HR - Sigurnosni naputci za elektromaterijal u sredini u kojoj prijeti opasnost od eksplozije. Ako Vam nije moguće čitati ovaj naputak, onda imate mogućnost da kod nas naručite naputak sastavljen na Vašem materinskom jeziku.

EU izjava o sukladnosti

Dobavljač Endress+Hauser jamči ovom izjavom i stavljanjem oznake CE da ovaj proizvod udovoljava zahtjevima europskih direktiva koje su na snazi. U izjavi o usuglašenosti se navode direktive, norme i dokumenti koji su na snazi.

HU - Biztonsági információk robbanásveszélyes területre való elektromos eszközökhöz. Amennyiben nem tudja elolvasni ezt az útmutatót, akkor megrendelheti az Ön anyanyelvére lefordítva is.

EU-megfelelőségi nyilatkozat

Az Endress+Hauser mint gyártó jelen megfeleléségi nyilatkozattal és a CE-jelzés felhelyezésével kijelenti, hogy ez a termék megfelel az alkalmazandó európai irányelveknek. Az alkalmazott irányelvek, szabványok és dokumentumok a megfeleléségi nyilatkozatban fel vannak tüntetve.

IT - Istruzioni di sicurezza per apparecchiature elettriche certificate per l'utilizzo in aree con pericolo di esplosione. Se il presente manuale non risulta comprensibile potete ordinarne una copia tradotta nella vostra lingua.

Dichiarazione di conformità UE

Con questa dichiarazione e con l'applicazione del marchio CE, il costruttore Endress+Hauser, assicura che il prodotto è conforme alle direttive europee vigenti. Prova della conformità è fornita dall'osservanza delle direttive, delle norme e dei documenti elencati.

LT - Elektros įrenginio saugumo nurodymai, susiję su sprogimo zonomis. Jeigu negalite perskaityti šios instrukcijos, kreipkitės į mus, kad užsisakytumėte į jūsų gimtąją kalbą išverstą instrukciją.

ES atitikties deklaracija

Gamintojas Endress+Hauser šia atitikties deklaracija ir CE ženkliniu patvirtina, kad gaminyje atitinka taikytinas ES direktyvas. Taikomos direktyvos, normos ir dokumentai yra pateikiami atitikties deklaracijoje.

LV - Drošības norādījumi elektrisko darba instrumentu lietošanai apgabalos, kas pakļauti sprādzienbīstamībai. Ja Jums nav iespēju izlasīt šos norādījumus, Jūs varat pasūtīt pie mums tulkojumu Jūsu valsts valodā.

ES atbilstības deklarācija

Ražotājs Endress+Hauser ar šo atbilstības apliecinājumu un CE zīmola lietojumu apstiprina, ka produkts izgatavots saskaņā ar atbilstošajām Eiropas vadlīnijām. Piemērotās vadlīnijas, normas un dokumenti atrunāti atbilstības apliecinājumā.

NL - Veiligheidsinstructies voor elektrisch materieel in explosiegevaarlijke omgeving. Wanneer u deze handleiding niet kunt lezen, kunt u een in uw landstaal vertaalde handleiding bij ons bestellen.

EU-conformiteitsverklaring

De leverancier Endress+Hauser waarborgt met deze verklaring en het aanbrengen van het CE-teken, dat dit product overeenstemt met de geldende Europese richtlijnen. De geldende richtlijnen, normen en documenten zijn aangegeven in de conformiteitsverklaring.

PL - Wskazówki dot. bezpieczeństwa dla urządzeń elektrycznych stosowanych w obszarze zagrożonym wybuchem. Jeśli niniejsza instrukcja napisana jest w języku, którym się nie posługujesz, możesz zamówić u nas przetłumaczony dokument.

Deklaracja zgodności UE

Producent Endress+Hauser w niniejszej deklaracji zgodności wraz z nadaniem znaku CE oświadcza, że produkt ten jest zgodny z obowiązującą Europejską Dyrektywą. Zastosowane wytyczne, normy oraz dokumenty podane są w deklaracji zgodności.

PT - Instruções de segurança para dispositivos eléctricos certificados para utilização em áreas de risco de incêndio. Se não compreender este manual, pode encomendar-nos directamente uma cópia na sua língua.

Declaração UE de conformidade

Com esta declaração de conformidade e a aplicação da marca CE, o fabricante Endress+Hauser, garante que o produto obedece às directivas europeias a aplicar. As directivas, normas e documentos são apresentadas na declaração de conformidade.

RO - Indicații de siguranță pentru mijloacele de producție electrice pentru zonele periclitare de explozie. Dacă nu puteți citi aceste instrucțiuni, atunci puteți comanda la noi instrucțiunile traduse în limba țării dumneavoastră.

Declarația UE de conformitate

Producătorul Endress+Hauser declară prin declarația de conformitate alăturată și prin aplicarea semnului CE că acest produs corespunde directivelor europene aplicabile. Directivele, normele aplicate și documentele sunt menționate în declarația de conformitate.

SK - Bezpečnostné pokyny pre elektrické zariadenie prevádzkované v priestoroch s nebezpečenstvom výbuchu. Ak nemáte možnosť 'prečítať' si tento návod, môžete si u nás objednať návod preložený do svojho jazyka.

EÚ vyhlásenie o zhode

Spoločnosť Endress+Hauser vyhlasuje prostredníctvom tohto vyhlásenia o konformite a použitím značky CE, že tento výrobok vyhovuje príslušným európskym smerniciam. Zmieňované smernice, normy a dokumenty sú uvedené vo Vyhlásení o konformite.

SL - Varnostni napotki glede električne opreme, namenjene za uporabo v eksplozivnih območjih. Če teh navodil ne morete razumeti, lahko pri nas naročite prevod v vaš jezik.

Izjava EU o skladnosti

Proizvajalec Endress+Hauser s to izjavo o skladnosti in navedbo oznake CE izjavlja, da je ta izdelek skladen s predpisanimi evropskimi smernicami. Upošteevane smernice, standardi in dokumenti so navedeni v izjavi o skladnosti.

SV - Säkerhetsföreskrifter för elektrisk utrustning certifierad för användning i explosionsfarliga områden. Om du inte förstår denna manual, kan en översatt kopia på ditt eget språk beställas från oss.

EU-försäkran om överensstämmelse

Endress+Hauser försäkrar med vidstående försäkran om överensstämmelse och med CE-märkningen att denna produkt överensstämmer med de tillämplbara europeiska riktlinjerna. De tillämplade riktlinjerna, normerna och dokumenten anges i försäkran om överensstämmelse.

Proline Promass 500

Table of contents

About this document 6

Associated documentation 6

Certificates and declarations 7

Manufacturer address 7

Extended order code 7

Safety instructions: General 12

Safety instructions: Installation 13

Temperature tables Proline 500 - digital 15

Temperature tables Proline 500 25

Connection values: Signal circuits 35

About this document

 The document number of these Safety Instructions (XA) must match the information on the nameplate.

Associated documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

- *Device Viewer* (www.endress.com/deviceviewer): Enter serial number from nameplate.
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

To commission the device, please observe the Operating Instructions pertaining to the device:

Measuring instrument	Documentation code			
	HART	FOUNDATION Fieldbus	PROFIBUS PA	PROFIBUS DP
Promass A 500 (8A5B)	BA01526D	BA01559D	BA01548D	–
Promass A 500 (8A5C)	BA01817D	BA01883D	BA01869D	BA01870D
Promass E 500	BA01528D	BA01561D	BA01550D	BA01872D
Promass F 500	BA01529D	BA01562D	BA01551D	BA01873D
Promass H 500	BA01530D	BA01563D	BA01552D	BA01874D
Promass I 500	BA01531D	BA01564D	BA01553D	BA01875D
Promass O 500	BA01532D	BA01565D	BA01554D	BA01876D
Promass P 500	BA01533D	BA01566D	BA01555D	BA01877D
Promass Q 500	BA01534D	BA01567D	BA01556D	BA01878D
Promass S 500	BA01535D	BA01568D	BA01557D	BA01879D
Promass X 500	BA01536D	BA01569D	BA01558D	BA01880D

Measuring instrument	Documentation code				
	Modbus RS485	Modbus over Ethernet-APL	EtherNet/IP	PROFINET	PROFINET over Ethernet-APL
Promass A 500 (8A5B)	BA01537D	–	BA01747D	BA01758D	–
Promass A 500 (8A5C)	BA01884D	BA02412D	BA01885D	BA01886D	BA02121D
Promass E 500	BA01539D	BA02414D	BA01749D	BA01760D	BA02124D
Promass F 500	BA01540D	BA02415D	BA01750D	BA01761D	BA02119D
Promass H 500	BA01541D	BA02416D	BA01751D	BA01762D	BA02125D
Promass I 500	BA01542D	BA02417D	BA01752D	BA01763D	BA02126D
Promass O 500	BA01543D	BA02418D	BA01753D	BA01764D	BA02127D

Measuring instrument	Documentation code				
	Modbus RS485	Modbus over Ethernet-APL	EtherNet/IP	PROFINET	PROFINET over Ethernet-APL
Promass P 500	BA01544D	BA02419D	BA01754D	BA01765D	BA02128D
Promass Q 500	BA01545D	BA02420D	BA01755D	BA01766D	BA02129D
Promass S 500	BA01546D	BA02421D	BA01756D	BA01767D	BA02130D
Promass X 500	BA01547D	BA02423D	BA01757D	BA01768D	BA02131D

Additional documentation

Contents	Document type	Documentation code
Explosion Protection	Brochure	CP00021Z/11
Ethernet-APL Installation Drawing	Installation Drawing	HE_01622

Please note the documentation associated with the device.

Certificates and declarations

EU Declaration of conformity

Documentation code: EC_00406

IEC Certificate of Conformity

Certificate number:

IECEX CSA 16.0034X

Affixing the certificate number certifies conformity with the standards under www.IECEX.com (depending on the device version).

- IEC 60079-0: 2017
- IEC 60079-7: 2017
- IEC 60079-11: 2011
- IEC 60079-15: 2017
- IEC TS 60079-47: 2021

Manufacturer address


Endress+Hauser Flowtec AG
Kägenstrasse 7
4153 Reinach BL
Switzerland

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional

information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code



Device type

The device and the device design is defined in the "Device type" section (Product root).

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).



More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Device type

Position	Order code for	Selected option	Description
1	Instrument family	8	Coriolis flowmeter
2	Sensor	A, E, F, H, I, O, P, Q, S, X ¹⁾	Sensor type
3	Transmitter	5	Transmitter type: 4-wire, remote version

Position	Order code for	Selected option	Description
4	Generation index	B, C	Platform generation
5, 6	Nominal diameter	Examples: 02, 04, 40, 50, 1H, 3E ²⁾ ³⁾	Nominal diameter of sensor

- 1)
- For replacement transmitter only: X
- 2)
- For the exact specification of the nominal diameter, see nameplate
- 3)
- For replacement transmitter only: XX

Proline 500 – digital	Proline 500
Order code for "Integrated ISEM Electronic", option A "Sensor"	Order code for "Integrated ISEM Electronic", option B "Transmitter"
 1 Transmitter 2 Connecting cable 3 Sensor connection housing with integrated ISEM	 1 Transmitter with integrated ISEM 2 Connecting cable 3 Sensor connection housing

Basic specifications

Position 1, 2 Order code for "Approval" Selected option	Position 10 Order code for "Integrated ISEM electronics" Selected option	Type of protection	
		Transmitter	Sensor
BL	A	Non-hazardous area ¹⁾	Ex ec IIC T5...T1 Gc or Ex ec nC IIC T5...T1 Gc ²⁾
BS	A	Ex ec nC IIC T5...T4 Gc ³⁾	Ex ec IIC T5...T1 Gc or Ex ec nC IIC T5...T1 Gc ²⁾
	B		Ex ec IIC T6...T1 Gc or Ex ec nC IIC T6...T1 Gc ²⁾

- 1) The transmitter is located in the non-hazardous area
- 2) The marking Ex ec nC is only applicable for sensor versions without purge connection or rupture disk. (see "Optional specifications").
- 3) The marking changes with order code "Output; input 1", option HA, MC, RC or TA: Ex ec nC [ic] IIC T5...T4 Gc

Position	Order code for	Selected option	Description
4, 5	Output; input 1	BA	4-20mA HART
		GA	PROFIBUS PA
		HA	PROFIBUS PA Ex-i
		LA	PROFIBUS DP
		MA	Modbus RS485
		MB	Modbus TCP over Ethernet-APL/SPE, 10Mbit/s
		MC	Modbus TCP over Ethernet-APL, Ex-i, 10Mbit/s
		NA	EtherNet/IP 2-port switch integrated
		RA	PROFINET IO 2-port switch integrated
		RB	PROFINET over Ethernet-APL/SPE, 10Mbit/s
		RC	PROFINET over Ethernet-APL, Ex-i, 10Mbit/s
		SA	FOUNDATION Fieldbus
		TA	FOUNDATION Fieldbus Ex-i
6	Output; input 2	A	W/o
		B	4-20mA
		C	4-20mA Ex-i passive
		D	Configurable I/O initial setting off
		E	Pulse/frequency/switch output

Position	Order code for	Selected option	Description
		F	Pulse output, phase-shifted
		G	Pulse/frequency/switch output Ex-i passive
		H	Relay
		I	4-20mA input
		J	Status input
7	Output; input 3	A	W/o
		B	4-20mA
		C	4-20mA Ex-i passive
		D	Configurable I/O initial setting off
		E	Pulse/frequency/switch output
		F	Pulse output, phase-shifted
		G	Pulse/frequency/switch output Ex-i passive
		H	Relay
		I	4-20mA input
		J	Status input
8	Output; input 4 ¹⁾	A	W/o
		B	4-20mA
		C	4-20mA Ex-i passive
		D	Configurable I/O initial setting off
		E	Pulse/frequency/switch output
		G	Pulse/frequency/switch output Ex-i passive
		H	Relay
		I	4-20mA input
		J	Status input
9	Display; Operation	F	4-line, illuminated; touch control
		G	4-line, illuminated; touch control + WLAN
10	Integrated ISEM Electronic	A	Sensor
		B	Transmitter
11	Transmitter Housing	A	Alu, coated
		D	Polycarbonate
		L	Cast, stainless

Position	Order code for	Selected option	Description
12	Sensor junction Housing	A	Alu, coated
		B	Stainless
		L	Cast, stainless
15, 16	Meas. Tube Mat., Wetted Parts Surface	LA	Stainl. steel, cryogenic -196°C/-320°F
21, 22	Device Model	A1	1
		A2	2

1) The order code "Output; input 4" is only available for the Proline 500 – digital transmitter.

Optional specifications

ID	Order code for	Selected option	Description
Cx	Sensor option	CA	Rupture disk
Cx	Sensor option	CG	Extended neck for insulation
Cx	Sensor option	CH	Purge connection
Px	Enclosed accessories	P8	Wireless antenna, wide area (external WLAN antenna) ¹⁾

1) The external WLAN antenna is available with the order code for "Accessory Enclosed", option P8.

Safety instructions:
General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations or guidelines (e.g. IEC/EN 60079-14)
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Use the device only in media where the wetted materials are known to be suitable.
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application, and the temperature classes.

- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- Observe all the technical data of the device (see nameplate).
- Avoid electrostatic charges which could result in electrostatic discharges while installing, operating, cleaning or maintaining:
 - For external non-metallic surfaces, e.g. housing, attached additional plates, RFID tag.
 - For attached external metallic parts that are not integrated into the local potential equalization system, e.g. nameplate tag, RFID tag.
 - Do not use in areas where the devices/electronic housing are exposed to highly charge-generating processes, pneumatically conveyed dusts and/or charge spraying in an electrostatic coating process.
 - Do not rub surfaces dry. Clean only with moist cloth.
 - Information on electrostatic hazards and how to minimize the generation of static electricity can be found in the technical specification IEC/TS 60079-32-1.

Safety instructions: Installation

General installation instructions

- Continuous service temperature of the connecting cable: -40 to +85 °C; but at least according to the operating temperature range of the application plus allowance for process conditions ($T_{a, \min}$ and $T_{a, \max} + 20 \text{ K}$).
- When the measuring device is connected, attention must be paid to the type of protection at the transmitter.
- For devices with order code "Sensor connection housing", option B: To maintain the required degree of ingress protection, ensure that the cover seal of the sensor connection housing is flat and free of bends or distortions before securing the cover. Replace any damaged or non-flat seals prior to reassembly.

Installation in potentially explosive atmospheres

- Do not disconnect the electrical connection of the power supply circuit when energized.
- Do not open the connection compartment cover when the device is energized.
- Connection to or operation with Service interface (Port 2) is not permitted.

Use of cable glands, sealing plugs and thread adapters

- Only use Ex certified cable glands, sealing plugs and thread adapters that are suitable for the intended application (see nameplates).
- Plastic sealing plugs are mounted to cable entries and metallic thread extensions for temporary protection during transport and storage. These must be replaced with suitable Ex certified cable entry devices for permanent use.
- The mounted metallic thread extensions and sealing plugs are tested and certified as part of the device. These meet the device's specific requirements.
- Supplied Ex cable glands are separately certified and meet the device's specific requirements.
- All unused cable entries must be closed with suitable Ex certified sealing plugs.
- Observe selection criteria for Ex cable entry devices as per IEC/EN 60079-14.

Ex ec type of protection

- Only use separately certified cable glands, sealing plugs and thread adapters (Ex ec IIC) which are suitable for operating temperatures from -40 °C to +85 °C and for IP 66/67.
- The mounted metallic thread extensions and sealing plugs are tested and certified as part of the devices for the type of protection Ex ec IIC.
- The cables must be routed such that they are securely seated, and sufficient strain relief must be ensured.

Optional external WLAN antenna

- Use only the external antenna (with or without extension cable) and the antenna feedthrough supplied by Endress+Hauser.
- The antenna feedthrough must be mounted to the transmitter with a tightening torque of 4 Nm.
Tightening torques for Polycarbonate transmitter housing: 2.5 Nm
- Use only an external antenna (with or without extension cable) equipped with a Type-N male connector (MIL-STD-348).
- The coupling nut of the Type-N male connector must be tightened by hand only.

Optional RFID TAG

- Do not use in areas with high electromagnetic field intensities.
- Avoid electrostatic charging.
- Ensure sufficient distance from processes generating high charges.

Intrinsic safety

- Observe the guidelines for interconnecting intrinsically safe circuits (e.g. IEC/EN 60079-14, IEC/EN 60079-25 , proof of intrinsic safety).
- The supplied connecting cable meets all the above requirements.

Potential equalization

- The device must be connected to the potential equalization system using designated protective ground terminals.
- It is also possible to integrate the device into the potential equalization system through a pipe system, provided that the pipe system meets the grounding requirements of applicable national regulations.

**Temperature
tables Proline 500
- digital**

Order code for "Integrated ISEM electronics", option A

NOTICE

In case of heating, risk of overheating.

- ▶ On devices with Heating jacket the corresponding temperature tables for devices with thermal insulation, are to be observed.
- ▶ Make sure that the heating medium, may not exceeded the maximum specified medium temperature of the exact used temperature classes of the device.

Minimum ambient temperature

$T_{a, \min} = -40\text{ }^{\circ}\text{C}$

Maximum ambient temperature

$T_{a, \max} = +60\text{ }^{\circ}\text{C}$ depending on temperature class, maximum medium temperature and device-specific features. See the corresponding temperature tables.

Transmitter: Non-hazardous area, Zone 2

Transmitter housing material	T _{a, max} [°C]			
	Non-hazardous area ¹⁾	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]
Aluminum	60	–	45	60
Polycarbonate	60	–	–	–

1) The transmitter is located in the non-hazardous area

Minimum medium temperature

- Promass A, F, H, I, P, Q, S, X:
T_{m, min} = -50 °C
- Promass E, O:
T_{m, min} = -40 °C
- Promass F, Q with cryogenic temperature version (order code for "Measuring tube material", option LA):
T_{m, min} = -196 °C

Maximum medium temperature without thermal insulation

Promass A (8A5B**-*)

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	60	–	95	130	170 ¹⁾	205	205

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass A (8A5C**-*)

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	55	–	95	130	170 ¹⁾	205	205
		60	–	95	130	170 ²⁾	190	190

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
2) The following applies for sensors with type of protection Ex ec nC: T_m = 190 °C

Promass E

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...15	150	60	–	75 ¹⁾	115 ²⁾	150	150	150
25...80	150	60	–	60 ¹⁾	95 ²⁾	140 ³⁾	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
3) The following applies for sensors with type of protection Ex ec nC: T_m = 150 °C

Promass F

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08...15	150	55	–	80 ²⁾	115 ³⁾	130	150	150
		60	–	80 ²⁾	115 ³⁾	130	130	130
	150 ⁴⁾	60	–	80 ²⁾	115 ³⁾	150	150	150
	240	60	–	80 ²⁾	115 ³⁾	170 ⁵⁾	240	240
25...80	150	55	–	60 ²⁾	95 ³⁾	150	150	150
		60	–	60 ²⁾	95 ³⁾	130	130	130
	150 ⁴⁾	60	–	60 ²⁾	95 ³⁾	150	150	150
	240	60	–	60 ²⁾	95 ³⁾	160 ⁵⁾	240	240
15, 25, 50... 250	350	50	–	85 ²⁾	120 ³⁾	185 ⁵⁾	280 ⁶⁾	350
		60	–	85 ²⁾	120 ³⁾	185 ⁵⁾	240 (275)	240 (350)
100...250	150	55	–	60 ²⁾	95 ³⁾	150	150	150
		60	–	60 ²⁾	95 ³⁾	130	130	130
	150 ⁴⁾	60	–	60 ²⁾	95 ³⁾	150	150	150
	240	60	–	60 ²⁾	95 ³⁾	160 ⁵⁾	240	240

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) Cryogenic temperature version: T_m = –196 to 150 °C
- 5) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
- 6) The following applies for sensors with type of protection Ex ec nC: T_m = 290 °C

Promass H

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	60	–	80 ²⁾	115 ³⁾	150	150	150
	205	60	–	80 ²⁾	115 ³⁾	165 ⁴⁾	205	205

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
15...50	150	60	–	60 ²⁾	95 ³⁾	130 ⁵⁾	150	150
	205	60	–	60 ²⁾	95 ³⁾	130 ⁴⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
- 5) The following applies for sensors with type of protection Ex ec nC: T_m = 150 °C

Promass I

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...80	150	55	–	60 ¹⁾	95 ²⁾	150	150	150
		60	–	60 ¹⁾	95 ²⁾	140	140	140

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C

Promass O

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80 ... 250	205	60	–	60 ¹⁾	95 ²⁾	160 ³⁾	205	205

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass P

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	60	–	80 ²⁾	115 ³⁾	150	150	150
	205	60	–	80 ²⁾	115 ³⁾	170 ⁴⁾	205	205

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
15...50	150	60	–	60 ²⁾	95 ³⁾	150	150	150
	205	60	–	60 ²⁾	95 ³⁾	160 ⁴⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass Q

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25 ... 250	205	60	–	60 ²⁾	95 ³⁾	160 ⁴⁾	205	205
	150 ⁵⁾	60	–	60 ²⁾	95 ³⁾	150	150	150

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
- 5) Cryogenic temperature version: T_m = -196 to 150 °C

Promass S

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	60	–	80 ¹⁾	115 ²⁾	150	150	150
15...50	150	60	–	60 ¹⁾	95 ²⁾	150	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C

Promass X

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	180	60	–	60 ¹⁾	95 ²⁾	160 ³⁾	180	180

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 180 °C

Maximum medium temperature with thermal insulation according to Endress+Hauser specifications

 For information on the thermal insulation of the device, see the "Thermal insulation" section of the "Operating instructions" document .

Promass A (8A5B**-*, 8A5C**-*)

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1 to 4	205	50	–	95	130	130	130	130

Promass E

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8 to 50	150	50	–	75 ¹⁾	115 ²⁾	150	150	150
80			–	60 ¹⁾	95 ²⁾	140 ³⁾	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 150 °C

Promass F

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08 to 15	150	45	–	80 ²⁾	115 ³⁾	150	150	150
		50	–	80 ²⁾	115 ³⁾	130	130	130
	150 ⁴⁾	50	–	80 ²⁾	115 ³⁾	150	150	150
	240	50	–	80 ²⁾	115 ³⁾	170 ⁵⁾	240	240
25 to 80	150	45	–	60 ²⁾	95 ³⁾	150	150	150
		50	–	60 ²⁾	95 ³⁾	130	130	130
	150 ⁴⁾	50	–	60 ²⁾	95 ³⁾	150	150	150
	240	50	–	60 ²⁾	95 ³⁾	160 ⁵⁾	240	240
15, 25, 50 to 250	350	50	–	85 ²⁾	120 ³⁾	185 ⁵⁾	280	350
100 to 250	150 ⁴⁾	45	–	60 ²⁾	95 ³⁾	150	150	150
		50	–	60 ²⁾	95 ³⁾	130	130	130

DN	$T_{m, \max \text{ range}}^{1)}$ [°C]	$T_{a, \max}$ [°C]	$T_{m, \max}$ [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
	150 ⁴⁾	50	–	60 ²⁾	95 ³⁾	150	150	150
	240	50	–	60 ²⁾	95 ³⁾	160 ⁵⁾	240	240

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: $T_m = 95$ °C
- 3) The following applies for sensors with type of protection Ex ec nC: $T_m = 130$ °C
- 4) Cryogenic temperature version: $T_m = -196$ to 150 °C
- 5) The following applies for sensors with type of protection Ex ec nC: $T_m = 195$ °C

Promass H

DN	$T_{m, \max \text{ range}}^{1)}$ [°C]	$T_{a, \max}$ [°C]	$T_{m, \max}$ [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	55	–	80 ²⁾	115 ³⁾	150	150	150
	205	55	–	80 ²⁾	115 ³⁾	165 ⁴⁾	205	205
15 to 50	150	55	–	60 ²⁾	95 ³⁾	130	150	150
	205	55	–	60 ²⁾	95 ³⁾	130 ⁴⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: $T_m = 95$ °C
- 3) The following applies for sensors with type of protection Ex ec nC: $T_m = 130$ °C
- 4) The following applies for sensors with type of protection Ex ec nC: $T_m = 195$ °C

Promass I

DN	$T_{m, \max \text{ range}}$ [°C]	$T_{a, \max}$ [°C]	$T_{m, \max}$ [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8 to 80	150	45	–	60 ¹⁾	95 ²⁾	150	150	150
		50	–	60 ¹⁾	95 ²⁾	130	130	130

- 1) The following applies for sensors with type of protection Ex ec nC: $T_m = 95$ °C
- 2) The following applies for sensors with type of protection Ex ec nC: $T_m = 130$ °C

Promass O

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80 to 250	205	55	–	60 ¹⁾	95 ²⁾	160 ³⁾	205	205

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass P

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	45	–	80 ²⁾	100 ³⁾	150	150	150
		50	–	80 ²⁾	100 ³⁾	130	130	130
	205	55	–	80 ²⁾	115 ³⁾	170 ⁴⁾	205	205
15 to 50	150	45	–	60 ²⁾	95 ³⁾	150	150	150
		50	–	60 ²⁾	95 ³⁾	130	130	130
	205	55	–	60 ²⁾	95 ³⁾	160 ⁴⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass Q

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25 to 250	205	50	–	60 ²⁾	95 ³⁾	160 ⁴⁾	205	205
25 to 250	150 ⁵⁾	50	–	60 ²⁾	95 ³⁾	150	150	150

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
- 5) Cryogenic temperature version: T_m = –196 to 150 °C

Promass S

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	45	–	80 ¹⁾	100 ²⁾	150	150	150
		50	–	80 ¹⁾	100 ²⁾	130	130	130
15 to 50	150	45	–	60 ¹⁾	95 ²⁾	150	150	150
		50	–	60 ¹⁾	95 ²⁾	130	130	130

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C


Promass X

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	180	55	–	60 ¹⁾	95 ²⁾	160 ³⁾	180	180

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
2) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
3) The following applies for sensors with type of protection Ex ec nC: T_m = 180 °C

**Maximum medium temperature for devices with thermal insulation
NOT in accordance with Endress+Hauser specifications**

The specified reference temperature T_{ref} and the maximum medium temperature T_{m, max} for each temperature class must not be exceeded.
→  20



A0031199

-  1 Position of reference point for temperature measurement
- A Standard version
- B Extended temperature version, cryogenic temperature version, high-temperature version
- 1 Reference point (T_{ref})

Reference temperature T_{ref}

T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
–	72	82	85	85	85

Temperature
tables Proline 500

Order code for "Integrated ISEM electronics", option B "Transmitter"

NOTICE

In case of heating, risk of overheating.

- ▶ On devices with Heating jacket the corresponding temperature tables for devices with thermal insulation, are to be observed.
- ▶ Make sure that the heating medium, may not exceeded the maximum specified medium temperature of the exact used temperature classes of the device.

Minimum ambient temperature

$T_{a, \min} = -40\text{ }^{\circ}\text{C}$

Maximum ambient temperature

$T_{a, \max} = +60\text{ }^{\circ}\text{C}$ depending on temperature class, maximum medium temperature and device-specific features. See the corresponding temperature tables.

Transmitter: Zone 2

$T_{a, \max}\text{ [}^{\circ}\text{C]}$		
T6 [85 °C]	T5 [100 °C]	T4 [135 °C]
-	45	60

Minimum medium temperature

- Promass A, F, H, I, P, Q, S, X:
 $T_{m, \min} = -50\text{ }^{\circ}\text{C}$
- Promass E, O:
 $T_{m, \min} = -40\text{ }^{\circ}\text{C}$
- Promass F, Q with cryogenic temperature version (order code for "Measuring tube material", option LA):
 $T_{m, \min} = -196\text{ }^{\circ}\text{C}$

Maximum medium temperature without thermal insulation

Promass A (8A5B**-*..., 8A5C**-*...)

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	205	50	50 ¹⁾	95	130	170 ²⁾	205	205
		60	– ¹⁾	95	130	170 ²⁾	205	205

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
2) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass E

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...15	150	45	45 ¹⁾	80 ²⁾	115 ³⁾	150	150	150
		60	– ¹⁾	80 ²⁾	115 ³⁾	150	150	150
25...80	150	60	– ¹⁾	60 ²⁾	95 ³⁾	140 ⁴⁾	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
4) The following applies for sensors with type of protection Ex ec nC: T_m = 150 °C

Promass F

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08...15	150	50	50	80	115	150	150	150
		60	– ²⁾	– ³⁾	115 ⁴⁾	150	150	150
	150 ⁵⁾	50	50	80	115	150	150	150
		60	– ²⁾	80 ³⁾	115 ⁴⁾	150	150	150
	240	50	50	80	115	170	240	240
		60	– ²⁾	80 ³⁾	115 ⁴⁾	170 ⁶⁾	240	240
25...80	150	45	60	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	150 ⁵⁾	45	60	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
	240	45	60	60	95	160	240	240
		60	– ²⁾	60 ³⁾	95 ⁴⁾	160 ⁶⁾	240	240
15, 25, 50... 250	350	60	70 ²⁾	85 ³⁾	120 ⁴⁾	185 ⁶⁾	280 ⁷⁾	350
100...250	150	45	60	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	150 ⁵⁾	45	60	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	240	45	60	60	95	160	240	240
		60	– ²⁾	60 ³⁾	95 ⁴⁾	160 ⁶⁾	240	240

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 5) Cryogenic temperature version: T_m = –196 to 150 °C
- 6) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
- 7) The following applies for sensors with type of protection Ex ec nC: T_m = 290 °C

Promass H

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	50	45	80	115	150	150	150
		60	– ²⁾	80 ³⁾	115 ⁴⁾	150	150	150
	205	50	45	80	115	165	205	205
		60	– ²⁾	80 ³⁾	115 ⁴⁾	165 ⁵⁾	205	205
15...50	150	60	– ²⁾	60 ³⁾	95 ⁴⁾	130	150	150
	205	60	– ²⁾	60 ³⁾	95 ⁴⁾	130 ⁵⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 5) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass I

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...80	150	45	45	60	95	150	150	150
		60	– ¹⁾	60 ²⁾	95 ³⁾	150	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C

Promass O

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80 ... 250	205	45	45	60	95	160	205	205
		60	– ¹⁾	60 ²⁾	95 ³⁾	160 ⁴⁾	205	205

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass P

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	45	45	80	115	150	150	150
		60	– ²⁾	80 ³⁾	115 ⁴⁾	150	150	150
	205	45	45	80	115	170	205	205
		60	– ²⁾	80 ³⁾	115 ⁴⁾	170 ⁵⁾	205	205
15...50	150	45	45	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	205	45	45	60	95	160	205	205
		60	– ²⁾	60 ³⁾	95 ⁴⁾	160 ⁵⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 5) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass Q

DN	$T_{m, \max \text{ range}}$ [°C]	$T_{a, \max}$ [°C]	$T_{m, \max}$ [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25 ... 250	205	45	45	60	95	160	205	205
		60	– ²⁾	60 ³⁾	95 ⁴⁾	160 ⁵⁾	205	205
	150 ⁶⁾	45	45	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: $T_m = 80$ °C
- 3) The following applies for sensors with type of protection Ex ec nC: $T_m = 95$ °C
- 4) The following applies for sensors with type of protection Ex ec nC: $T_m = 130$ °C
- 5) The following applies for sensors with type of protection Ex ec nC: $T_m = 195$ °C
- 6) Cryogenic temperature version: $T_m = -196$ to 150 °C

Promass S

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	45	45	80	115	150	150	150
		60	– ¹⁾	80 ²⁾	115 ³⁾	150	150	150
15...50		45	45	60	95	150	150	150
		60	– ¹⁾	60 ²⁾	95 ³⁾	150	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: $T_m = 80$ °C
- 2) The following applies for sensors with type of protection Ex ec nC: $T_m = 95$ °C
- 3) The following applies for sensors with type of protection Ex ec nC: $T_m = 130$ °C

Promass X

DN	$T_{m, \max \text{ range}}$ [°C]	$T_{a, \max}$ [°C]	$T_{m, \max}$ [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	180	45	45	60	95	160	180	180
		60	– ¹⁾	60 ²⁾	95 ³⁾	160 ⁴⁾	180	180

- 1) The following applies for sensors with type of protection Ex ec nC: $T_m = 80$ °C
- 2) The following applies for sensors with type of protection Ex ec nC: $T_m = 95$ °C
- 3) The following applies for sensors with type of protection Ex ec nC: $T_m = 130$ °C
- 4) The following applies for sensors with type of protection Ex ec nC: $T_m = 180$ °C

Maximum medium temperature with thermal insulation according to Endress+Hauser specifications

 For information on the thermal insulation of the device, see the "Thermal insulation" section of the "Operating instructions" document .

Promass A (8A5B**-*, 8A5C**-*...)

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1 to 4	205	50	50 ¹⁾	95	130	150	150 (180)	150 (180)
		60	–	95	130	150	150	150

1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C

Promass E

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8 to 15	150	45	45	80	115	150	150	150
		60	– ¹⁾	80 ²⁾	115 ³⁾	150	150	150
25 to 50		60	– ¹⁾	60 ²⁾	95 ³⁾	140 ⁴⁾	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 150 °C

Promass F

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08 to 15	150	50	50	80	115	150	150	150
		60	– ²⁾	80 ³⁾	115 ⁴⁾	150	150	150
	150 ⁵⁾	50	50	80	115	150	150	150
		60	– ²⁾	80 ³⁾	115 ⁴⁾	150	150	150
	240	50	50	80	115	170	240	240
		60	– ²⁾	80 ³⁾	115 ⁴⁾	170 ⁶⁾	240	240
25 to 80	150	45	60	60	95	150	150	150

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
	150 ⁵⁾	60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
		45	60	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	240	45	60	60	95	160	240	240
		60	– ²⁾	60 ³⁾	130 ³⁾	160 ⁶⁾	240	240
	350	60	70 ²⁾	85 ³⁾	120 ⁴⁾	185 ⁶⁾	280 ⁷⁾	350
15, 25, 50 to 250	150	45	60	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	150 ⁵⁾	45	60	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	240	45	60	60	95	160 ⁶⁾	240	240
		60	– ²⁾	60 ³⁾	95 ⁴⁾	160 ⁶⁾	240	240

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 5) Cryogenic temperature version: T_m = –196 to 150 °C
- 6) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
- 7) The following applies for sensors with type of protection Ex ec nC: T_m = 290 °C

Promass H

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	50	45	80	115	150	150	150
		60	– ²⁾	80 ³⁾	115 ⁴⁾	150	150	150
	205	50	45	80	115	165	205	205
		60	– ²⁾	80 ³⁾	115 ⁴⁾	165 ⁵⁾	205	205
15 to 50	150	60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	205	60	– ²⁾	60 ³⁾	95 ⁴⁾	130 ⁵⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 5) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass I

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8 to 80	150	45	45	60	95	150	150	150
		60	– ¹⁾	60 ²⁾	95 ³⁾	150	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C

Promass O

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80 to 250	205	45	45	60	95	160	205	205
		60	– ¹⁾	60 ²⁾	95 ³⁾	160 ⁴⁾	205	205

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass P

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	45	45	80	115	150	150	150
		60	– ²⁾	80 ³⁾	115 ⁴⁾	150	150	150
	205	45	45	80	115	170	205	205
		60	– ²⁾	80 ³⁾	115 ⁴⁾	170 ⁵⁾	205	205
15 to 50	150	45	45	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150
	205	45	45	60	95	160	205	205
		60	– ²⁾	60 ³⁾	95 ⁴⁾	160 ⁵⁾	205	205

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 5) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C

Promass Q

DN	T _{m, max range} ¹⁾ [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25 to 250	205	45	45	60	95	160	205	205
		60	– ²⁾	60 ³⁾	95 ⁴⁾	160 ⁵⁾	205	205
	150 ⁶⁾	45	45	60	95	150	150	150
		60	– ²⁾	60 ³⁾	95 ⁴⁾	150	150	150

- 1) Maximum temperature range, see nameplate
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 5) The following applies for sensors with type of protection Ex ec nC: T_m = 195 °C
- 6) Cryogenic temperature version: T_m = –196 to 150 °C

Promass S

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	150	45	45	80	115	150	150	150
		60	– ¹⁾	80 ²⁾	115 ³⁾	150	150	150
15 to 50	150	45	45	60	95	150	150	150
		60	– ¹⁾	60 ²⁾	95 ³⁾	150	150	150

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C


Promass X

DN	T _{m, max range} [°C]	T _{a, max} [°C]	T _{m, max} [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	180	45	45	60	95	160	180	180
		60	– ¹⁾	60 ²⁾	95 ³⁾	160 ⁴⁾	180	180

- 1) The following applies for sensors with type of protection Ex ec nC: T_m = 80 °C
- 2) The following applies for sensors with type of protection Ex ec nC: T_m = 95 °C
- 3) The following applies for sensors with type of protection Ex ec nC: T_m = 130 °C
- 4) The following applies for sensors with type of protection Ex ec nC: T_m = 180 °C

**Maximum medium temperature for devices with thermal insulation
NOT in accordance with Endress+Hauser specifications**

The specified reference temperature T_{ref} and the maximum medium temperature $T_{m, max}$ for each temperature class must not be exceeded.
→  30



A0031199

-  2 *Position of reference point for temperature measurement*
- A *Standard version*
- B *Extended temperature version, cryogenic temperature version, high-temperature version*
- 1 *Reference point (T_{ref})*

Reference temperature T_{ref}

T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
69	72	84	91	91	91

Connection
values: Signal
circuits

The following tables contain specifications which are dependent on the transmitter type and its input and output assignment. Compare the following specifications with those on the nameplate of the transmitter.

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

Supply voltage		Input/output 1 (port 1)		Input/output 2		Input/output 3		Input/output 4 ¹⁾		Service interface (Port 2)
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.										

1) Input/output only available for Proline 500 - digital.

FOUNDATION fieldbus

Supply voltage		Input/output 1 (port 1)		Input/output 2		Input/output 3		Input/output 4 ¹⁾		Service interface (Port 2)
1 (+)	2 (-)	26 (A)	27 (B)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.										

1) Input/output only available for Proline 500 - digital.

PROFIBUS DP

Supply voltage		Input/output 1 (port 1)		Input/output 2		Input/output 3		Input/output 4 ¹⁾		Service interface (Port 2)
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.										

1) Input/output only available for Proline 500 - digital.

PROFIBUS PA

Supply voltage		Input/output 1 (port 1)		Input/output 2		Input/output 3		Input/output 4 ¹⁾		Service interface (Port 2)
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.										

1) Input/output only available for Proline 500 - digital.

Modbus RS485

Supply voltage		Input/output 1 (port 1)		Input/output 2		Input/output 3		Input/output 4 ¹⁾		Service interface (Port 2)
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.										

1) Input/output only available for Proline 500 - digital.

Modbus TCP

Supply voltage		Input/output 1 (Port 1 ¹⁾)		Input/output 2		Input/output 3		Input/output 4 ²⁾		Service interface (Port 2) ¹⁾
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.										

- 1) For Modbus TCP communication, either port 1 OR port 2 can be used.
2) Input/output only available for Proline 500 - digital.

PROFINET

Supply voltage		Input/output 1 (Port 1) ¹⁾	Input/output 2		Input/output 3		Input/output 4 ²⁾		Service interface (Port 2) ¹⁾
1 (+)	2 (-)	RJ45	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.									

- 1) Port can be used for communication or as a service interface (CDI-RJ45).
2) Input/output only available for Proline 500 - digital.

PROFINET over Ethernet-APL

Supply voltage		Input/output 1 (Port 1)		Input/output 2		Input/output 3		Input/output 4 ¹⁾		Service interface (Port 2 ²⁾)
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.										

1) Input/output only available for Proline 500 - digital.

2) No PROFINET communication available on port 2

Ethernet/IP

Supply voltage		Input/output 1 (Port 1) ¹⁾	Input/output 2		Input/output 3		Input/output 4 ²⁾		Service interface (Port 2) ¹⁾
1 (+)	2 (-)	RJ45	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)	CDI-RJ45
Device-specific terminal assignment: adhesive label in terminal cover.									

1) Port can be used for communication or as a service interface (CDI-RJ45).

2) Input/output only available for Proline 500 - digital.

Safety-related values

Order code for "Output; input 1"	Output type	Safety-related values	
		Output; input 1 (Port 1)	Service interface (Port 2)
Option BA	Current output 4-20 mA HART	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$
Option GA	PROFIBUS PA	$U_N = 32 V_{DC}$ $U_M = 250 V_{AC}$	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$
Option LA	PROFIBUS DP	$U_N = 5 V$ $U_M = 250 V_{AC}$	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$
Option MA	Modbus RS485	$U_N = 5 V$ $U_M = 250 V_{AC}$	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$
Option MB	Modbus TCP over Ethernet- APL 10 Mbit/s, SPE 10 Mbit/s, Ethernet 100 Mbit/s	APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$
Option NA	EtherNet/IP	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$
Option RA	PROFINET	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$	$U_N = 3.3 V_{AC}$ $U_M = 250 V_{AC}$

Order code for "Output; input 1"	Output type	Safety-related values	
		Output; input 1 (Port 1)	Service interface (Port 2)
Option RB	PROFINET over Ethernet- APL/SPE, 10Mbit/s	APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$	$U_N = 3.3\text{ V}_{AC}$ $U_M = 250\text{ V}_{AC}$
Option SA	FOUNDATION Fieldbus	$U_N = 32\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$	$U_N = 3.3\text{ V}_{AC}$ $U_M = 250\text{ V}_{AC}$

Order code for "Output; input 2" "Output; input 3" "Output; input 4"	Output type	Safety-related values		
		Output; input 2	Output; input 3	Output; input 4
Option B	Current output 4-20 mA	$U_N = 30\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$		
Option D	Configurable I/O initial setting off	$U_N = 30\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$		
Option E	Pulse/frequency/switch output	$U_N = 30\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$		
Option F	Double pulse output	$U_N = 30\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$		
Option H	Relay output	$U_N = 30\text{ V}_{DC}$ $I_N = 100\text{ mA}_{DC}/500\text{ mA}_{AC}$ $U_M = 250\text{ V}_{AC}$		
Option I	Current input 4-20 mA	$U_N = 30\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$		
Option J	Status input	$U_N = 30\text{ V}_{DC}$ $U_M = 250\text{ V}_{AC}$		

Intrinsically safe values

Order code for "Output; input 1"	Output type	Intrinsically safe values Output; input 1 (Port 1)
Option HA	PROFIBUS PA Ex i (STANDARD + FISCO)	Ex ic $U_i = 32 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8.5 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$
Option MC	Modbus TCP over Ethernet- APL, Ex-i, 10Mbit/s	2-WISE power load, APL port profile SLAC ¹⁾ Ex ic $U_i = 17.5 \text{ V}$ $I_i = 380 \text{ mA}$ $P_i = 5.32 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$ Cable specifications according to 2-WISE: $R_c = 15 \text{ to } 150 \text{ } \Omega/\text{km}$ $L_c = 0.4 \text{ to } 1 \text{ mH/km}$ $C_c = 45 \text{ to } 200 \text{ nF/km}$ $C_c = C_c \text{ line/line} + 0,5 C_c \text{ line/screen}$, if both lines are floating, or $C_c = C_c \text{ line/line} + C_c \text{ line/screen}$, if the screen is connected to one line Length of cable (not including cable stubs): $\leq 200 \text{ m (656.2 ft)}$ Length of cable stubs: $\leq 1 \text{ m (3.3 ft)}$
Option RC	PROFINET over Ethernet- APL, Ex-i, 10Mbit/s	
Option TA	FOUNDATION Fieldbus Ex i (STANDARD + FISCO)	Ex ic $U_i = 32 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8.5 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$

1) For further options see Ethernet-APL Installation Drawing HE_01622.

Order code for "Output; input 2" "Output; input 3" "Output; input 4"	Output type	Intrinsically safe values		
		Output; input 2	Output; input 3	Output; input 4
Option C	Current output 4-20mA Ex-i passive	Ex ic U _i = 30 V I _i = 100 mA P _i = 1.25 W L _i = 0 C _i = 0		
Option G	Pulse/frequency/switch output Ex-i passive	Ex ic U _i = 30 V I _i = 100 mA P _i = 1.25 W L _i = 0 C _i = 0		



71713408

www.addresses.endress.com
