

# Safety Instructions

## Liquiphant FTL62

Ex ia IIC T6...T1 Ga/Gb

Ex ia IIC T6...T1 Gb



---

# Liquiphant FTL62

## Table of contents

About this document ..... 4

Associated documentation ..... 4

Supplementary documentation ..... 4

Certificates and declarations ..... 4

Manufacturer address ..... 4

Extended order code ..... 4

Safety instructions: General ..... 9

Safety instructions: Specific conditions of use ..... 10

Safety instructions: Installation ..... 11

Safety instructions: Zone 0 ..... 13

Safety instructions: Zone separation Zone 0, Zone 1 ..... 14

Temperature tables ..... 14

Connection data ..... 21

**About this document**

The document number of these Safety Instructions (XA) must match the information on the nameplate.

**Associated documentation**

All documentation is available on the Internet:

[www.endress.com/Deviceviewer](http://www.endress.com/Deviceviewer)

(enter the serial number from the nameplate).

To commission the device, please observe the Operating Instructions pertaining to the device:

BA02036F

**Supplementary documentation**

Explosion protection brochure: CP00021Z

The explosion protection brochure is available on the Internet:

[www.endress.com/Downloads](http://www.endress.com/Downloads)

**Certificates and declarations****Certificate of Conformity**

Certificate number:

Production Maulburg, Germany  
TÜV 23.1271 X

Production Itatiba, Brazil  
TÜV 19.1701 X

Production Greenwood, Indiana, USA  
TÜV 23.1272 X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- ABNT NBR IEC 60079-0:2020
- ABNT NBR IEC 60079-11:2013
- ABNT NBR IEC 60079-26:2022

**Manufacturer address**

Endress+Hauser SE+Co. KG  
Hauptstraße 1  
79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

**Extended order code**

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional

information about the nameplate is provided in the associated Operating Instructions.

### Structure of the extended order code

FTL62	–	*****	+	A*B*C*D*E*F*G*..
(Device type)		(Basic specifications)		(Optional specifications)

\* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

#### *Basic specifications*

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

#### *Optional specifications*

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

### Extended order code: Liquiphant



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

#### *Device type*

FTL62

Basic specifications

Position 1, 2 (Approval)		
Selected option		Description
FTL62	MB <sup>1)</sup>	INMETRO Ex ia IIC T6...T1 Ga/Gb
		INMETRO Ex ia IIC T6...T1 Gb


- 1)
- In connection with Position 3, 4 = A8 and Optional specification, ID Nx, Ox = NG:  
The temperature classes change to T4...T1

Position 3, 4 (Output)		
Selected option		Description
FTL62	A7	FEL67, 2-wire PFM + test button
	A8	FEL68, 2-wire NAMUR + test button
	GA	FEL60D, density/concentration

Position 6 (Housing, Material)		
Selected option		Description
FTL62	A	Single compartment; plastic
	B	Single compartment; Alu, coated
	C	Single compartment; 316L, cast
	D	Single compartment; 316L, hygiene
	M	Dual compartment L-shape; Alu, coated



Shown in the temperature tables  
exemplary as follows:





Position 7 (Electrical Connection)		
Selected option		Description
FTL62	A	Gland M20, plastic, IP66/68 NEMA Type 4X/6P
	B <sup>1)</sup>	Gland M20, brass nickel plated, IP66/68 NEMA Type 4X/6P
	C <sup>2)</sup>	Gland M20, 316L, IP66/68 NEMA Type 4X/6P
	F	Thread M20, IP66/68 NEMA Type 4X/6P
	G	Thread G1/2, IP66/68 NEMA Type 4X/6P
	H <sup>3)</sup>	Thread NPT1/2, IP66/68 NEMA Type 4X/6P
	I <sup>4)</sup>	Thread NPT3/4, IP66/68 NEMA Type 4X/6P
	J	Gland M20, plastic blue, IP66/68 NEMA Type 4X/6P
	M <sup>4)</sup>	Plug M12, IP66/67 NEMA Type 4X
	Y	Special version: Thread NPT1/2, IP66/68 NEMA Type 4X/6P

- 1) Only in connection with Position 6 = B, M  
 2) Only in connection with Position 6 = B, C  
 3) Only in connection with Position 6 = A  
 4) Only in connection with Position 6 = B, C, M

Position 8 (Application)		
Selected option		Description
FTL62	C <sup>1)</sup>	Process max 80°C/176°F, max 25bar
	N <sup>2)</sup>	Process max 120°C/248°F, max 40bar (ECTFE)
	P <sup>2)</sup>	Process max 150°C/302°F, max 40bar (PFA)
	T <sup>2)</sup>	Process max 150°C/302°F, max 25bar (Enamel)

- 1) Only in connection with Position 3, 4 = GA  
 2) Only in connection with Position 3, 4 = A7, A8

Position 9 (Surface Refinement)		
Selected option		Description
FTL62	N	Coating ECTFE
	P	Coating PFA (Edlon)
	Q	Coating PFA (RubyRed)
	R	Coating PFA (conductive)
	T	Coating Enamel

Position 10 (Type of Probe)		
Selected option		Description
FTL62	2	Extension tube
	3	Short tube version
<div>  <p>Shown in the temperature tables exemplary as follows:</p> </div> <div>  </div>		

*Optional specifications*

ID Jx, Kx (Test, Certificate, Declaration)		
Selected option		Description
FTL62	JL <sup>1)</sup>	Ambient temperature -50°C/-58°F

- 1) Only in connection with Position 3, 4 = A7, A8, Position 6 = B, C, M, Position 7 = B, C, F, G, I, Y

ID Mx (Sensor Design)		
Selected option		Description
FTL62	MA	Sensor remote, cable TPR, 2m/80in + mounting bracket, wall/pipe, 316L
	MB	Sensor remote, cable TPR, 5m/200in + mounting bracket, wall/pipe, 316L
	MC	Sensor remote, cable TPR, 10m/400in + mounting bracket, wall/pipe, 316L
	MD	Sensor remote, cable TPR, 20m/800in + mounting bracket, wall/pipe, 316L
	ME	Sensor remote, cable TPR, 30m/1200in + mounting bracket, wall/pipe, 316L
	MR	Temperature separator
	MS	Pressure tight feed through (Second line of defence)



ID Nx, Ox (Accessory Mounted)		
Selected option		Description
FTL62	NF <sup>1)</sup>	Bluetooth
	NG <sup>2)</sup>	Bluetooth for NAMUR output
	NJ	Cover with sight glass, glass
	NK	Cover with sight glass, plastic

- 1) Only in connection with Position 3, 4 = A7, Position 6 = A, B, M  
 2) Only in connection with Position 3, 4 = A8, Position 6 = A, B, M

ID Px, Rx (Accessory Enclosed)		
Selected option		Description
FTL62	PA <sup>1)</sup>	Weather protection cover, 316L
	PB <sup>2)</sup>	Weather protection cover, plastic
	R6 <sup>3)</sup>	Test magnet

- 1) Only in connection with Position 6 = M  
 2) Only in connection with Position 6 = B, C  
 3) Only in connection with Position 3, 4 = A8

## Safety instructions:


### General

- The device is intended to be used in explosive atmospheres as defined in the scope of IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Devices suitable for zone separation (marked Ga/Gb or Da/Db) are always suitable for installation in the less critical zone (Gb or Db). Due to space limitations the corresponding marking maybe not indicated on the nameplate.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.

- Avoid electrostatic charging:
  - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ...)
  - Of isolated capacities (e.g. isolated metallic plates)
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application and the temperature class.
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.

**Safety  
instructions:  
Specific  
conditions of use**

Permitted ambient temperature range at the electronics enclosure:  
 $-40\text{ °C} \leq T_a \leq +70\text{ °C}$

- Limitations of the maximum ambient temperature at the electronics enclosure may be required dependent on device configuration, process temperatures and temperature classification.
- Details of limitations: →  14, "Temperature tables".
- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
  - Observe the danger of electrostatic charging and discharge.
  - Do not install in the vicinity of processes ( $\leq 0.5\text{ m}$ ) generating strong electrostatic charges.

*Basic specification, Position 6 = A*

Avoid electrostatic charging of the enclosure (e.g. friction, cleaning, maintenance, strong medium flow).

*Basic specification, Position 6 = B, M*

Avoid sparks caused by impact and friction.

*Optional specification, ID Px, Rx = PA*

Connect the weather protection cover to the local potential equalization.

*Optional specification, ID Px, Rx = PB*

Avoid electrostatic charging of the weather protection cover (e.g. friction, cleaning, maintenance, strong medium flow).

*Optional specification, ID Px, Rx = R6*

Suitable for use in explosion hazardous areas.

## Device group IIC/IIB


Basic specification, Position 9 = N, P, Q

- Probes can be used in gases of Group IIC if avoiding electrostatic charging (e.g. through friction, cleaning, maintenance, strong medium flow). These probes are marked by the warning sign "Avoid Electrostatic Charge".
- If electrostatic charging cannot be avoided: Probe can be used in gases of Group IIB.

Basic specification, Position 9 = R, T


Due to the surface resistance 1 GΩ ([R] PFA-conductive) or the enamel (glass) surface, these coatings are suitable without restrictions.

## Safety instructions: Installation



- A Zone 1
- 1 Tank; Zone 0, Zone 1
- 2 Electronic insert
- 3 Enclosure
- 4 Basic specification, Position 3, 4 = A7, A8:  
Associated intrinsically safe power supply units  
Basic specification, Position 3, 4 = GA:  
Only associated intrinsically safe power supply unit FML621 from  
Endress+Hauser
- 5 Potential equalization line
- 6 Local potential equalization

Optional specification, ID Mx = MA - ME



A0055812

- A Zone 1  
 1 Tank; Zone 0, Zone 1  
 2 Sensor enclosure  
 3 Electronic insert  
 4 Electronics enclosure  
 5 Basic specification, Position 3, 4 = A7, A8:  
 Associated intrinsically safe power supply units  
 Basic specification, Position 3, 4 = GA:  
 Only associated intrinsically safe power supply unit FML621 from  
 Endress+Hauser  
 6 Potential equalization line  
 7 Local potential equalization

- When the device is connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC and IIB, the type of protection changes to Ex ib IIC and Ex ib IIB.
- Continuous service temperature of the connecting cable:  $\geq T_a + 20 \text{ K}$ .
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- Observe the maximum process conditions according to the manufacturer's Operating Instructions.
- At high medium temperatures, note flange pressure load capacity as a factor of temperature.

- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.
- Support extension tube of the device if a dynamic load is expected.
- The device can be equipped with the Bluetooth® module: refer to the Operating Instructions and specifications in the "Bluetooth® module" chapter.

### Intrinsic safety

- The device is only suitable for connection to certified, intrinsically safe equipment with explosion protection Ex ia / Ex ib.
- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least 500 V<sub>rms</sub>.

### Potential equalization

Integrate the device into the local potential equalization.

*Optional specification, ID Px, Rx = PA*

Connect the weather protection cover to the local potential equalization.

### Bluetooth® module

*Basic specification, Position 3, 4 = A7*

If the device is equipped with the Bluetooth® module, no battery is required or allowed.

*Basic specification, Position 3, 4 = A8*

- If the device is equipped with the Bluetooth® module, a battery is required.
- Removal or replacement of the battery is only permitted in non-hazardous areas.
- Connection or disconnection of the Bluetooth® module is permitted in hazardous areas.

*Only use one of the following battery types:*

Manufacturer	Battery type
Tadiran	SL-360/S
XENO ENERGY	ER14505 / XL-060F

### Safety instructions: Zone 0

When using under non-atmospheric pressures and non-atmospheric temperatures: The sensor part of the device approved for Zone 0 does not cause any ignition hazards.

**Safety instructions:**  
**Zone separation**  
**Zone 0, Zone 1**

The zone separation wall of the device is made of stainless steel or high corrosion-resistant alloy of thickness  $\geq 1$  mm.

**Temperature tables**

**i** *Optional specification, ID Jx, Kx = JL*  
Lower limit of the ambient temperature for explosion protection changes to  $-50^{\circ}\text{C}$ .

**General notes**

**i** *Optional specification, ID Px, Rx = PB*  
When using the weather protection cover: Reduce the values  $T_a$  of P1, P2, P3 by 16 K.

**Description notes**


**i** Unless otherwise indicated, the positions always refer to the basic specification.

1st column: Position 8 = A, B, ...


2nd column: Temperature classes T6 ( $85^{\circ}\text{C}$ ) to T1 ( $450^{\circ}\text{C}$ )

Column P1 to P5: Position (temperature value) on the axes of the derating

- $T_a$ : Ambient temperature in  $^{\circ}\text{C}$
- $T_p$ : Process temperature in  $^{\circ}\text{C}$



Zone 0, Zone 1



Position 3, 4 = A7

 In connection with Position 8 = N:  $T_{p\_max} = 120\text{ }^{\circ}\text{C}$

Without Optional specification, ID Mx = MR, MS

A, B		P1		P2		P3		P4		P5	
		T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>
	T6	-50	70	73	70 65 <sup>1)</sup>	80 70 <sup>1)</sup>	67	80 70 <sup>1)</sup>	-40 -50 <sup>2)</sup>	-50	-40 -50 <sup>2)</sup>
	T5	-50	70	94	70 62 <sup>1)</sup>	95 94 <sup>1)</sup>	70 62 <sup>1)</sup>	95 94 <sup>1)</sup>		-50	
	T4	-50	70	94	70 62 <sup>1)</sup>	130 125 <sup>1)</sup>	55 50 <sup>1)</sup>	130 125 <sup>1)</sup>		-50	
	T3...T1	-50	70	94	70 62 <sup>1)</sup>	150 140 <sup>1)</sup>	47 40 <sup>1)</sup>	150 140 <sup>1)</sup>		-50	

- 1) Only in connection with Position 6 = D
- 2) Only in connection with Optional specification, ID Jx, Kx = JL

With Optional specification, ID Mx = MR, MS

A, B		P1		P2		P3		P4		P5	
		T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>
	T6	-50	70	80 79 <sup>1)</sup>	70 65 <sup>1)</sup>	80 79 <sup>1)</sup>	70 65 <sup>1)</sup>	80 79 <sup>1)</sup>	-40 -50 <sup>2)</sup>	-50	-40 -50 <sup>2)</sup>
	T5	-50	70	95 94 <sup>1)</sup>	70	95 94 <sup>1)</sup>	70	95		-50	
	T4	-50	70	130 94 <sup>1)</sup>	70	130	70 65 <sup>1)</sup>	130		-50	
	T3...T1	-50	70	150 94 <sup>1)</sup>	70	150	70 62 <sup>1)</sup>	150		-50	

- 1) Only in connection with Position 6 = D
- 2) Only in connection with Optional specification, ID Jx, Kx = JL



Position 3, 4 = A8



In connection with Position 8 = N:  $T_{p\_max} = 120\text{ °C}$

Without Optional specification, ID Mx = MR, MS

A, B		P1		P2		P3		P4		P5	
		$T_p$	$T_a$	$T_p$	$T_a$	$T_p$	$T_a$	$T_p$	$T_a$	$T_p$	$T_a$
	T6 <sup>1)</sup>	-50	70	80	70	80	70	80	-40 -50 <sup>2)</sup>	-50	-40
	T5 <sup>1)</sup>	-50	70	95	70	95	70	95		-50	-50 <sup>2)</sup>
	T4	-50	70	115 70 <sup>1)</sup>	70	130 120 <sup>1)</sup> 125 <sup>3)</sup>	62 50 <sup>1)</sup> 59 <sup>1) + 3)</sup>	130		-50	
	T3...T1	-50	70	115 70 <sup>1)</sup>	70	150 120 <sup>1)</sup> 142 <sup>3)</sup>	54 50 <sup>1)</sup> 59 <sup>1) + 3)</sup>	150		-50	

- 1) Only in connection with Optional specification, ID Nx, Ox = NG: Temperature classes only valid for T4...T1
- 2) Only in connection with Optional specification, ID Jx, Kx = JL
- 3) Only in connection with Position 6 = D

With Optional specification, ID Mx = MR, MS

A, B		P1		P2		P3		P4		P5	
		$T_p$	$T_a$	$T_p$	$T_a$	$T_p$	$T_a$	$T_p$	$T_a$	$T_p$	$T_a$
	T6 <sup>1)</sup>	-50	70	80	70	80	70	80	-40 -50 <sup>2)</sup>	-50	-40
	T5 <sup>1)</sup>	-50	70	95	70	95	70	95		-50	-50 <sup>2)</sup>
	T4	-50	70 65 <sup>1)</sup>	130	70 65 <sup>1)</sup>	130	70 65 <sup>1)</sup>	130		-50	
	T3...T1	-50	70 63 <sup>1)</sup>	150	70 63 <sup>1)</sup>	150	70 63 <sup>1)</sup>	150		-50	

- 1) Only in connection with Optional specification, ID Nx, Ox = NG: Temperature classes only valid for T4...T1
- 2) Only in connection with Optional specification, ID Jx, Kx = JL

Position 3, 4 = GA

Without Optional specification, ID Mx = MR, MS


C		P1		P2		P3		P4		P5	
		T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>
	T6	-50	69 62 <sup>1)</sup>	80	69 62 <sup>1)</sup>	80	69 62 <sup>1)</sup>	80	-40	-50	-40
	T5...T1	-50	70	80	70	80	70	80	-40	-50	-40

1) Only in connection with Position 6 = D

With Optional specification, ID Mx = MR, MS

C		P1		P2		P3		P4		P5	
		T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>
	T6	-50	70 66 <sup>1)</sup>	80	70 66 <sup>1)</sup>	80	70 66 <sup>1)</sup>	80	-40	-50	-40
	T5...T1	-50	70	80	70	80	70	80	-40	-50	-40

1) Only in connection with Position 6 = D



Position 3, 4 = A7



In connection with Position 8 = N:  $T_{p\_max} = 120\text{ °C}$

Optional specification, ID Mx = MA - ME without Optional specification, ID Mx = MR, MS

A, B		P1			P2			P3			P4		P5	
		$T_p$	$T_a^{1)}$	$T_a^{2)}$	$T_p$	$T_a^{1)}$	$T_a^{2)}$	$T_p$	$T_a^{1)}$	$T_a^{2)}$	$T_p$	$T_a$	$T_p$	$T_a$
	T6	-50	70	70	80	70 68 <sup>3)</sup>	70	80	70 68 <sup>3)</sup>	70	80	-40 -50 <sup>4)</sup>	-50	-40 -50 <sup>4)</sup>
	T5	-50	70	90	95	70	90	95	70	90	95		-50	
	T4	-50	70	90	130	70	90	130	70	90	130		-50	
	T3...T1	-50	70	75	150	70	75	150	70	75	150		-50	

- 1) Electronics enclosure (A)
- 2) Sensor enclosure (B)
- 3) Only in connection with Position 6 = D
- 4) Only in connection with Optional specification, ID Jx, Kx = JL

Optional specification, ID Mx = MA - ME with Optional specification, ID Mx = MR, MS

A, B		P1			P2			P3			P4		P5	
		$T_p$	$T_a^{1)}$	$T_a^{2)}$	$T_p$	$T_a^{1)}$	$T_a^{2)}$	$T_p$	$T_a^{1)}$	$T_a^{2)}$	$T_p$	$T_a$	$T_p$	$T_a$
	T6	-50	70	70	80	70 68 <sup>3)</sup>	70	80	70 68 <sup>3)</sup>	70	80	-40 -50 <sup>4)</sup>	-50	-40 -50 <sup>4)</sup>
	T5	-50	70	90	95	70	90	95	70	90	95		-50	
	T4	-50	70	90	130	70	90	130	70	90	130		-50	
	T3...T1	-50	70	90	150	70	90	150	70	90	150		-50	

- 1) Electronics enclosure (A)
- 2) Sensor enclosure (B)
- 3) Only in connection with Position 6 = D
- 4) Only in connection with Optional specification, ID Jx, Kx = JL

Position 3, 4 = A8

 In connection with Position 8 = N: T<sub>p\_max</sub> = 120 °C

Optional specification, ID Mx = MA - ME without Optional specification, ID Mx = MR, MS

A, B		P1			P2			P3			P4		P5	
		T <sub>p</sub>	T <sub>a</sub> <sup>1)</sup>	T <sub>a</sub> <sup>2)</sup>	T <sub>p</sub>	T <sub>a</sub> <sup>1)</sup>	T <sub>a</sub> <sup>2)</sup>	T <sub>p</sub>	T <sub>a</sub> <sup>1)</sup>	T <sub>a</sub> <sup>2)</sup>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>
	T6 <sup>3)</sup>	-50	70	70	80	70	70	80	70	70	80	-40 -50 <sup>4)</sup>	-50	-40
	T5 <sup>3)</sup>	-50	70	90	95	70	90	95	70	90	95		-50	-50 <sup>4)</sup>
	T4	-50	70 69 <sup>3)</sup>	90	130	70 69 <sup>3)</sup>	90	130	70 69 <sup>3)</sup>	90	130		-50	
	T3...T1	-50	70 69 <sup>3)</sup>	75	150	70 69 <sup>3)</sup>	75	150	70 69 <sup>3)</sup>	75	150		-50	

- 1) Electronics enclosure (A)
- 2) Sensor enclosure (B)
- 3) Only in connection with Optional specification, ID Nx, Ox = NG: Temperature classes only valid for T4...T1
- 4) Only in connection with Optional specification, ID Jx, Kx = JL

Optional specification, ID Mx = MA - ME with Optional specification, ID Mx = MR, MS

A, B		P1			P2			P3			P4		P5	
		T <sub>p</sub>	T <sub>a</sub> <sup>1)</sup>	T <sub>a</sub> <sup>2)</sup>	T <sub>p</sub>	T <sub>a</sub> <sup>1)</sup>	T <sub>a</sub> <sup>2)</sup>	T <sub>p</sub>	T <sub>a</sub> <sup>1)</sup>	T <sub>a</sub> <sup>2)</sup>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>
	T6 <sup>3)</sup>	-50	70	70	80	70	70	80	70	70	80	-40 -50 <sup>4)</sup>	-50	-40
	T5 <sup>3)</sup>	-50	70	90	95	70	90	95	70	90	95		-50	-50 <sup>4)</sup>
	T4	-50	70 69 <sup>3)</sup>	90	130	70 69 <sup>3)</sup>	90	130	70 69 <sup>3)</sup>	90	130		-50	
	T3...T1	-50	70 69 <sup>3)</sup>	90	150	70 69 <sup>3)</sup>	90	150	70 69 <sup>3)</sup>	90	150		-50	

- 1) Electronics enclosure (A)
- 2) Sensor enclosure (B)
- 3) Only in connection with Optional specification, ID Nx, Ox = NG: Temperature classes only valid for T4...T1
- 4) Only in connection with Optional specification, ID Jx, Kx = JL

Position 3, 4 = GA

With Optional specification, ID Mx = MA - ME

C		P1		P2		P3		P4		P5	
		T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>	T <sub>p</sub>	T <sub>a</sub>
	T6	-50	70	80	70	80	70	80	-40	-50	-40
	T5...T1	-50	70	80	70	80	70	80	-40	-50	-40

Connection data

Optional specification, ID Nx, Ox = NF, NG

When using the Bluetooth® module: No changes to the connection values.

Associated intrinsically safe power supply unit with max. electrical specifications below the characteristic values of the electronic inserts

Basic specification, Position 3, 4	Power supply circuit
A7	U <sub>i</sub> = 14.6 V I <sub>i</sub> = 100 mA P <sub>i</sub> = 633 mW L <sub>i</sub> = 0 C <sub>i</sub> = 3 nF
A8	U <sub>i</sub> = 16 V I <sub>i</sub> = 52 mA P <sub>i</sub> = 170 mW L <sub>i</sub> = 0 C <sub>i</sub> = 30 nF

Only associated intrinsically safe power supply unit FML621 from Endress+Hauser

Basic specification, Position 3, 4	Power supply circuit
GA	U <sub>i</sub> = 27.6 V I <sub>i</sub> = 93 mA P <sub>i</sub> = 640 mW L <sub>i</sub> = 3 µH C <sub>i</sub> = 3 nF

---

---



71673885

[www.addresses.endress.com](http://www.addresses.endress.com)

---