

Technical Information

Cerabar PMC51B

Process pressure and level measurement in liquids or gases

4-20mA analog, 4-20mA HART,
PROFINET over Ethernet-APL



Digital pressure transmitter with ceramic process membrane

Application

- Pressure measuring ranges: up to 40 bar (600 psi)
- Completely vacuum resistant: up to +100 °C (212 °F) process temperature
- Accuracy: up to $\pm 0.055\%$

Advantages

The new Cerabar generation introduces a robust pressure transmitter that combines numerous benefits: Easiest local or remote operation, allows condition-based maintenance and offers smart safety in processes. The firmware is designed to ensure extremely easy handling. Intuitive and clear wizard navigation guides the user through the commissioning and verification of the device. The Bluetooth connectivity provides safe and remote operation. The large display guarantees excellent readability. The device features a ceramic membrane for abrasive, corrosive or vacuum applications with integrated membrane breakage diagnostic.

Table of contents

About this document	4	Storage temperature	27
Symbols	4	Operating altitude	27
Graphic conventions	4	Climate class	27
List of abbreviations	5	Degree of protection	27
Turn down calculation	5	Vibration resistance	28
		Electromagnetic compatibility (EMC)	28
Function and system design	6	Process	29
Equipment architecture	6	Process temperature range	29
Measuring system	6	Thermal shock	30
Communication and data processing	7	Process pressure range	30
Reliability for devices with HART, Bluetooth, PROFINET over Ethernet-APL	7	Ultrapure gas applications	31
		Steam applications and saturated steam applications	31
Input	8	Mechanical construction	32
Measured variable	8	Design dimensions	32
Measuring range	8	Dimensions	33
		Weight	44
Output	10	Materials in contact with process	45
Output signal	10	Materials not in contact with process	46
Signal on alarm	10	Accessories	47
Load	10		
Damping	11	Operability	48
Ex connection data	11	Operating concept (not for devices with 4 to 20 mA analog)	48
Linearization	11	Local operation	48
Protocol-specific data	11	Local display	49
Wireless HART data	14	Remote operation	50
		System integration	52
Power supply	15	Supported operating tools	52
Terminal assignment	15		
Available device plugs	15	Certificates and approvals	53
Supply voltage	17	CE mark	53
Electrical connection	18	RCM-Tick marking	53
Potential equalization	18	Ex approvals	53
Terminals	18	Sanitary compatibility	53
Cable entries	18	EAC conformity	53
Cable specification	19	Drinking water approval	53
Overvoltage protection	19	Overfill protection system	53
		Functional safety SIL/ IEC 61508 Declaration of Conformity	53
Performance characteristics	20	Marine approval	54
Response time	20	Radio approval	54
Reference operating conditions	20	CRN approval	54
Total performance	20	Test reports	54
Resolution	21	Pressure Equipment Directive 2014/68/EU (PED)	54
Total error	22	Oxygen application (optional)	55
Long-term stability	22	China RoHS symbol	55
Response time T63 and T90	22	RoHS	55
Installation factors	23	PROFINET over Ethernet-APL certification	55
Warm-up time	23	Additional certification	55
		Order information	56
Installation	24	Ordering information	56
Orientation	24	Scope of delivery	56
Installation instructions	24	Service	56
Sensor selection and arrangement	24	Measuring point (TAG)	56
Special mounting instructions	25	Test reports, declarations and inspection certificates	57
Environment	27		
Ambient temperature range	27		

Accessories 58
Device-specific accessories 58
Device Viewer 58

Documentation 58

Registered trademarks 59

About this document

Symbols

Warning symbols



This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.



This symbol alerts you to a potentially dangerous situation. Failure to avoid this situation can result in serious or fatal injury.



This symbol alerts you to a potentially dangerous situation. Failure to avoid this situation can result in minor or medium injury.



This symbol alerts you to a potentially harmful situation. Failure to avoid this situation can result in damage to the product or something in its vicinity.

Electrical symbols

Ground connection: \perp

Terminal for connection to the grounding system.

Symbols for certain types of Information

Permitted:

Procedures, processes or actions that are permitted.

Forbidden:

Procedures, processes or actions that are forbidden.

Additional information:

Reference to documentation:

Reference to page:

Series of steps: 1., 2., 3.

Result of an individual step:

Symbols in graphics

Item numbers: 1, 2, 3 ...

Series of steps: 1., 2., 3.

Views: A, B, C, ...

Symbols on the device

Safety instructions: →


Observe the safety instructions contained in the associated Operating Instructions.

Graphic conventions



- Installation, explosion and electrical connection drawings are presented in simplified format
- Devices, assemblies, components and dimensional drawings are presented in reduced-line format
- Dimensional drawings are not to-scale representations; the dimensions indicated are rounded off to 2 decimal places


List of abbreviations



A0029505

- 1 OPL: The OPL (over pressure limit = measuring cell overpressure limit) for the device depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection must be taken into consideration in addition to the measuring cell. Observe pressure-temperature dependency. OPL (Over Pressure Limit) is a test pressure.
 - 2 MWP: The MWP (maximum working pressure) for the measuring cells depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection also has to be taken into consideration besides the measuring cell. Observe pressure-temperature dependency. The maximum working pressure may be applied at the device for an unlimited period of time. The maximum working pressure can be found on the nameplate.
 - 3 The maximum measuring range corresponds to the span between the LRL and URL. This measuring range is equivalent to the maximum span that can be calibrated/adjusted.
 - 4 The calibrated/adjusted span corresponds to the span between the LRV and URV. Factory setting: 0 to URL. Other calibrated spans can be ordered as customized spans.
- p Pressure
LRL Lower range limit
URL Upper range limit
LRV Lower range value
URV Upper range value
TD Turn down Example - see the following section.

Turn down calculation



A0029545

- 1 Calibrated/adjusted span
- 2 Zero point-based span
- 3 Upper range limit

Example:


- Measuring cell: 10 bar (150 psi)
- Upper range limit (URL) = 10 bar (150 psi)
- Calibrated/adjusted span: 0 to 5 bar (0 to 75 psi)
- Lower range value (LRV) = 0 bar (0 psi)
- Upper range value (URV) = 5 bar (75 psi)

$$TD = \frac{URL}{|URV - LRV|}$$

In this example, the TD is therefore 2:1. This measuring span is based on the zero point.

Function and system design

Equipment architecture



A0043088

- 1 Atmospheric pressure (gauge pressure measuring cell)
- 2 Ceramic meter body
- 3 Electrodes
- 4 Ceramic membrane
- 5 Seal
- p* Pressure


The ceramic measuring cell (Ceraphire®) is an oil-free measuring cell. The pressure acts directly on the robust ceramic membrane and causes it to deflect. A pressure-dependent change in capacitance is measured at the electrodes of the ceramic meter body and the membrane. The measuring range is determined by the thickness of the ceramic membrane.

Advantages:

- High overload resistance
- Thanks to ultrapure 99.9 % ceramic
 - Extremely high chemical durability
 - Resistant to abrasion and corrosion
 - High mechanical durability
- Suitable for vacuum applications

Measuring system

Level measurement (level, volume and mass):



A0038343

- h* Height (level)
- p* Pressure
- ρ* Density of the medium
- g* Acceleration due to gravity

Advantages:

- Volume and mass measurements in any vessel shape with a freely programmable characteristic curve
- Has a wide range of uses, e.g.
 - For foam formation
 - In vessels with agitators or screen fittings
 - For liquid gases

Communication and data processing	<ul style="list-style-type: none">■ 4-20 mA analog (optional)■ 4 to 20 mA with HART communication protocol (optional)■ Bluetooth (optional)■ PROFINET over Ethernet-APL (optional): 10BASE-T1L communication protocol
Reliability for devices with HART, Bluetooth, PROFINET over Ethernet-APL	IT security <p>Endress+Hauser can only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings. IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.</p>

Input

Measured variable	Measured process variables <ul style="list-style-type: none"> ■ Absolute pressure ■ Gauge pressure
Measuring range	Depending on the device configuration, the maximum working pressure (MWP) and the overpressure limit (OPL) can deviate from the values in the tables.

Absolute pressure

Measuring cell	Maximum measuring range		Smallest calibratable span (preset at factory) ¹⁾	
	lower (LRL)	upper (URL)		
	[bar _{abs} (psi _{abs})]	[bar _{abs} (psi _{abs})]	[bar (psi)]	Platinum
100 mbar (1.5 psi)	0	+0.1 (+1.5)	0.005 (0.075) ²⁾	20 mbar (0.3 psi)
250 mbar (3.75 psi)	0	+0.25 (+3.75)	0.005 (0.075) ³⁾	50 mbar (1 psi)
400 mbar (6 psi)	0	+0.4 (+6)	0.005 (0.075) ⁴⁾	80 mbar (1.2 psi)
1 bar (15 psi)	0	+1 (+15)	0.01 (0.15) ⁵⁾	200 mbar (3 psi)
2 bar (30 psi)	0	+2 (+30)	0.02 (0.3) ⁵⁾	400 mbar (6 psi)
4 bar (60 psi)	0	+4 (+60)	0.04 (0.6) ⁵⁾	800 mbar (12 psi)
10 bar (150 psi)	0	+10 (+150)	0.1 (1.5) ⁵⁾	2 bar (30 psi)
40 bar (600 psi)	0	+40 (+600)	0.4 (6) ⁵⁾	8 bar (120 psi)

- 1) The maximum TD is 5:1 in the case of platinum.
2) Largest factory-configurable turn down: 20:1
3) Largest factory-configurable turn down: 50:1
4) Largest factory-configurable turn down: 80:1
5) Largest factory-configurable turn down: 100:1

Absolute pressure

Measuring cell	MWP	OPL	Vacuum resistance	Burst pressure ¹⁾
	[bar _{abs} (psi _{abs})]	[bar _{abs} (psi _{abs})]	[bar _{abs} (psi _{abs})]	[bar (psi)]
100 mbar (1.5 psi)	2.7 (40.5)	4 (60)	0	4 (60)
250 mbar (3.75 psi)	3.3 (49.5)	5 (75)	0	5 (75)
400 mbar (6 psi)	5.3 (79.5)	8 (120)	0	8 (120)
1 bar (15 psi)	6.7 (100.5)	10 (150)	0	10 (150)
2 bar (30 psi)	12 (180)	18 (270)	0	18 (270)
4 bar (60 psi)	16.7 (250.5)	25 (375)	0	25 (375)
10 bar (150 psi)	26.7 (400.5)	40 (600)	0	40 (600)
40 bar (600 psi)	40 (600)	60 (900)	0	60 (900)

- 1) The information applies to the standard device (without a diaphragm seal).

Gauge pressure

Measuring cell	Maximum measuring range		Smallest calibratable span (preset at factory) ¹⁾	
	lower (LRL)	upper (URL)		
	[bar (psi)]	[bar (psi)]	[bar (psi)]	Platinum
100 mbar (1.5 psi)	-0.1 (-1.5)	+0.1 (+1.5)	0.005 (0.075) ²⁾	20 mbar (0.3 psi)
250 mbar (3.75 psi)	-0.25 (-3.75)	+0.25 (+3.75)	0.005 (0.075) ³⁾	50 mbar (1 psi)

Measuring cell	Maximum measuring range		Smallest calibratable span (preset at factory) ¹⁾	
	lower (LRL)	upper (URL)		
	[bar (psi)]	[bar (psi)]	[bar (psi)]	Platinum
400 mbar (6 psi)	-0.4 (-6)	+0.4 (+6)	0.005 (0.075) ⁴⁾	80 mbar (1.2 psi)
1 bar (15 psi)	-1 (-15)	+1 (+15)	0.01 (0.15) ⁵⁾	200 mbar (3 psi)
2 bar (30 psi)	-1 (-15)	+2 (+30)	0.02 (0.3) ⁵⁾	400 mbar (6 psi)
4 bar (60 psi)	-1 (-15)	+4 (+60)	0.04 (0.6) ⁵⁾	800 mbar (12 psi)
10 bar (150 psi)	-1 (-15)	+10 (+150)	0.1 (1.5) ⁵⁾	2 bar (30 psi)
40 bar (600 psi)	-1 (-15)	+40 (+600)	0.4 (6) ⁵⁾	8 bar (120 psi)

- 1) The maximum TD is 5:1 in the case of platinum.
- 2) Largest factory-configurable turn down: 20:1
- 3) Largest factory-configurable turn down: 50:1
- 4) Largest factory-configurable turn down: 80:1
- 5) Largest factory-configurable turn down: 100:1

Gauge pressure

Measuring cell	MWP	OPL	Vacuum resistance	Burst pressure ¹⁾
	[bar (psi)]	[bar (psi)]	[bar _{abs} (psi _{abs})]	[bar (psi)]
100 mbar (1.5 psi)	2.7 (40.5)	4 (60)	0.7 (10.5)	4 (60)
250 mbar (3.75 psi)	3.3 (49.5)	5 (75)	0.5 (7.5)	5 (75)
400 mbar (6 psi)	5.3 (79.5)	8 (120)	0	8 (120)
1 bar (15 psi)	6.7 (100.5)	10 (150)	0	10 (150)
2 bar (30 psi)	12 (180)	18 (270)	0	18 (270)
4 bar (60 psi)	16.7 (250.5)	25 (375)	0	25 (375)
10 bar (150 psi)	26.7 (400.5)	40 (600)	0	40 (600)
40 bar (600 psi)	40 (600)	60 (900)	0	60 (900)

- 1) The information applies to the standard device (without a diaphragm seal).

Output

Output signal

Current output

4 to 20 mA analog, 2-wire

4 to 20 mA with superimposed digital communication protocol HART, 2-wire

The current output offers a choice of three different operating modes:

- 4.0 to 20.5 mA
- NAMUR NE 43: 3.8 to 20.5 mA (factory setting)
- US mode: 3.9 to 20.8 mA

PROFINET with Ethernet-APL


10BASE-T1L, 2-wire 10 Mbit

Signal on alarm

- 4 to 20 mA analog:
 - Signal over-range: > 20.5 mA
 - Signal under-range: < 3.8 mA
 - Min alarm (< 3.6 mA, factory setting)
- 4 to 20 mA HART:
 - Options:
 - Max alarm: can be set from 21.5 to 23 mA
 - Min. alarm: < 3.6 mA (factory setting)
 - Signal on alarm in accordance with NAMUR recommendation NE 43.
- PROFINET over Ethernet-APL:
 - According to "Application layer protocol for decentralized periphery", Version 2.4
 - Diagnostics according to PROFINET PA Profile 4.02

Load


4 to 20 mA analog



A0039234

- 1 10.5 to 35 V power supply
 2 R_{Lmax} maximum load resistance
 U_B Supply voltage

4 to 20 mA HART



- 1 Power supply 10.5 to 30 VDC Ex i
2 Power supply 10.5 to 35 VDC, for other types of protection and non-certified device versions
3 R_{Lmax} maximum load resistance
 U_B Supply voltage

 Operation via handheld terminal or PC with operating program: take minimum communication resistance of 250 Ω into consideration.

Damping	<p>A damping affects all outputs (output signal, display). Damping can be enabled as follows:</p> <ul style="list-style-type: none"> ■ Via the DIP switch on the electronic insert (analog electronics only) ■ Factory setting: 1 s 						
Ex connection data	<p>See the separate technical documentation (Safety Instructions (XA)) on www.endress.com/download.</p>						
Linearization	<p>The device's linearization function allows the user to convert the measured value to any units of height or volume. User-defined linearization tables of up to 32 value pairs can be entered if necessary.</p>						
Protocol-specific data	<p>HART</p> <ul style="list-style-type: none"> ■ Manufacturer ID: 17 (0x11{hex}) ■ Device type ID: 0x112A ■ Device revision: 1 ■ HART specification: 7 ■ DD revision: 1 ■ Device description files (DTM, DD) information and files at: <ul style="list-style-type: none"> ■ www.endress.com ■ www.fieldcommgroup.org ■ HART load: min. 250 Ohm <p><i>HART device variables (preset at the factory)</i></p> <p>The following measured values are assigned to the device variables at the factory:</p> <table border="1"> <thead> <tr> <th>Device variable</th><th>Measured value</th></tr> </thead> <tbody> <tr> <td>Primary variable (PV) ¹⁾</td><td>Pressure ²⁾</td></tr> <tr> <td>Secondary variable (SV)</td><td>Sensor temperature</td></tr> </tbody> </table>	Device variable	Measured value	Primary variable (PV) ¹⁾	Pressure ²⁾	Secondary variable (SV)	Sensor temperature
Device variable	Measured value						
Primary variable (PV) ¹⁾	Pressure ²⁾						
Secondary variable (SV)	Sensor temperature						

Device variable	Measured value
Tertiary variable (TV)	Electronic temperature
Quaternary variable (QV)	Sensor pressure ³⁾

- 1) The PV is always applied to the current output.
- 2) The pressure is the calculated signal after damping and position adjustment.
- 3) The Sensor pressure is the raw signal of the measuring cell before damping and position adjustment.

Choice of HART device variables


- **Pressure** option (after position correction and damping)
 - Scaled variable
 - Sensor temperature
 - Sensor pressure
 - Sensor Pressure is the raw signal from sensor before damping and position adjustment.
 - Electronics temperature
 - Percent of range
 - Loop current
 - The loop current is the output current set by the applied pressure.

Supported functions

- Burst mode
- Additional transmitter status
- Device locking

PROFINET over Ethernet-APL

Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.4
Communication type	Ethernet Advanced Physical Layer 10BASE-T1L
Conformity class	Conformance Class B
Netload Class	Netload Class II
Baud rates	Automatic 10 Mbit/s with full-duplex detection
Periods	From 32 ms
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Media Redundancy Protocol (MRP)	Yes
System redundancy support	System redundancy S2 (2 AR with 1 NAP)
Device profile	Application interface identifier 0xB310 Generic device
Manufacturer ID	0x11
Device type ID	A22A
Device description files (GSD, FDI, DTM, DD)	Information and files at: <ul style="list-style-type: none"> ■ www.endress.com On the product page for the device: Documents/Software → Device drivers ■ www.profibus.org
Supported connections	<ul style="list-style-type: none"> ■ 2 x AR (IO Controller AR) ■ 1 x AR (IO-Supervisor Device AR connection allowed) ■ 1 x Input CR (Communication Relation) ■ 1 x Output CR (Communication Relation) ■ 1 x Alarm CR (Communication Relation)
Configuration options for device	<ul style="list-style-type: none"> ■ Manufacturer-specific software (FieldCare, DeviceCare) ■ Web browser ■ Device master file (GSD), can be read out via the integrated web server of the device ■ DIP switch for setting the service IP address

Configuration of the device name	<ul style="list-style-type: none"> ■ DCP protocol ■ Process Device Manager (PDM) ■ Integrated web server
Supported functions	<ul style="list-style-type: none"> ■ Identification & maintenance Simple device identification via: <ul style="list-style-type: none"> ■ Control system ■ Nameplate ■ Measured value status The process variables are communicated with a measured value status ■ Blinking feature via the local display for simple device identification and assignment ■ Device operation via operating tools (e.g. FieldCare, DeviceCare, SIMATIC PDM)
System integration	<p>For information on system integration, see  Operating Instructions</p> <ul style="list-style-type: none"> ■ Cyclic data transmission ■ Overview and description of the modules ■ Status coding ■ Startup parameterization ■ Factory setting

PROFIBUS PA

Manufacturer ID:

17 (0x11)

Ident number:

Profile version:

3.02

GSD file and version

Information and files at:

- www.endress.com

On the product page for the device: Documents/Software → Device drivers


- www.profibus.com

Output values

Analog Input:

- Pressure
- Scaled variable
- Sensor temperature
- Sensor pressure
- Electronics temperature
- **Median of pressure signal** option (only available if the "Heartbeat Verification + Monitoring" application package was selected).
- **Noise of pressure signal** option (only available if the "Heartbeat Verification + Monitoring" application package was selected).

Digital Input:

 Only available if the "Heartbeat Verification + Monitoring" application package was selected

Heartbeat Technology → SSD: Statistical Sensor Diagnostics

Heartbeat Technology → Process Window

Input values

Analog Output:

Analog value from PLC to be indicated on the display

Supported functions

- Identification & maintenance
 - Simple device identification via control system and nameplate
- Automatic Ident Number Adoption
 - GSD compatibility mode for generic profile 0x9700 "Transmitter with 1 Analog Input"
- Physical Layer Diagnostics
 - Installation check of the PROFIBUS segment and device using terminal voltage and message monitoring
- PROFIBUS upload/download
 - Reading and writing parameters is up to ten times faster with PROFIBUS upload/download
- Condensed status
 - Straightforward and self-explanatory diagnostic information through categorization of occurring diagnostic messages


Wireless HART data


- Minimum starting voltage: 10.5 V
- Start-up current: 3.6 mA
- Start-up time: <5 s
- Minimum operating voltage: 10.5 V
- Multidrop current: 4 mA

Power supply

Terminal assignment

Single compartment housing




 1 Connection terminals and ground terminal in the connection compartment


1 Plus terminal

2 Minus terminal

3 Internal ground terminal

Dual-compartment housing



 2 Connection terminals and ground terminal in the connection compartment

1 Plus terminal

2 Minus terminal

3 Internal ground terminal


Available device plugs



In the case of devices with a plug, it is not necessary to open the housing for connection purposes.

Use the enclosed seals to prevent the penetration of moisture into the device.

Devices with valve plug



A0023097


3 BN = brown, BU = blue, GNYE = green/yellow

A Electrical connection for devices with valve connector

B View of the plug-in connection on the device

Material: PA 6.6

Devices with M12 plug



A0011175

4 View of the plug-in connection on the device

Pin	Analog HART
1	Signal +
2	Not used
3	Signal -
4	Earth

Pin	PROFINET over Ethernet-APL
1	APL signal -
2	APL signal +
3	Shielding
4	Not used

Endress+Hauser offers the following accessories for devices with an M12 plug:

Plug-in jack M 12x1, straight

■ Material:

Body: PBT; union nut: nickel-plated die-cast zinc; seal: NBR

■ Degree of protection (fully locked): IP67

■ Order number: 52006263

Plug-in jack M 12x1, angled (not for PROFINET over Ethernet-APL)

■ Material:

Body: PBT; union nut: nickel-plated die-cast zinc; seal: NBR


■ Degree of protection (fully locked): IP67

■ Order number: 71114212

Cable 4x0.34 mm² (20 AWG) with M12 plug-in jack, elbowed, screw plug, length 5 m (16 ft)

- Material: body: TPU; union nut: nickel-plated die-cast zinc; cable: PVC
- Degree of protection (fully locked): IP67/68
- Order number: 52010285
- Cable colors
 - 1 = BN = brown
 - 2 = WT = white
 - 3 = BU = blue
 - 4 = BK = black

Devices with a Harting plug Han7D



A Electrical connection for devices with Harting plug Han7D

B View of the plug-in connection on the device

- Brown

≡ Green/yellow

+ Blue

Material: CuZn, gold-plated contacts of the plug-in jack and plug

Supply voltage

- Analog/HART: Ex d, Ex e, non-Ex: supply voltage: 10.5 to 35 V_{DC}
- Analog/HART: Ex i: supply voltage: 10.5 to 30 V_{DC}
- HART: Nominal current: 4 to 20 mA HART
- PROFINET over Ethernet-APL: APL power class A (9.6 to 15 V_{DC} 540 mW)

A suitable circuit breaker should be provided for the device in accordance with IEC/EN 61010.


i Analog/HART: The power unit must be tested to ensure it meets safety requirements (e.g. PELV, SELV, Class 2) and must comply with the relevant protocol specifications. For 4 to 20 mA, the same requirements apply as for HART.

i PROFINET over Ethernet-APL: The APL field switch must be tested to ensure it meets safety requirements (e.g. PELV, SELV, Class 2) and must comply with the relevant protocol specifications.

Electrical connection

Connection examples

PROFINET over Ethernet-APL



A0045802


5 Connection example for PROFINET over Ethernet-APL

- 1 Automation system
- 2 APL field switch
- 3 Observe cable specifications
- 4 Transmitter

Potential equalization

- i** If necessary, the potential matching line can be connected to the outer ground terminal of the device before the device is connected.
- i** For optimum electromagnetic compatibility:
 - Use the shortest possible potential matching line.
 - Ensure a cross-section of at least 2.5 mm² (14 AWG).


Single-compartment housing



A0045411

- 1 Ground terminal for connecting the potential matching line

Dual-compartment housing



A0045412

- 1 Ground terminal for connecting the potential matching line

Terminals

- Supply voltage and inner ground terminal
Clamping range: 0.5 to 2.5 mm² (20 to 14 AWG)
- External ground terminal
Clamping range: 0.5 to 4 mm² (20 to 12 AWG)


Cable entries

The type of cable entry depends on the device version ordered.

- i** Always route connecting cables downwards so that moisture cannot penetrate the connection compartment.

If necessary, create a drip loop or use a weather protection cover.


Single-compartment housing



A0045413

- 1 Cable entry
- 2 Blind plug

Dual-compartment housing



A0045414

- 1 Cable entry
- 2 Blind plug

Cable specification

- The cable outer diameter depends on the cable entry used
- Cable outer diameter
 - Plastic: Ø5 to 10 mm (0.2 to 0.38 in)
 - Nickel-plated brass: Ø7 to 10.5 mm (0.28 to 0.41 in)
 - Stainless steel: Ø7 to 12 mm (0.28 to 0.47 in)

PROFINET with Ethernet-APL

The reference cable type for APL segments is fieldbus cable type A, MAU type 1 and 3 (specified in IEC 61158-2). This cable meets the requirements for intrinsically safe applications according to IEC TS 60079-47 and can also be used in non-intrinsically safe applications.

Cable type	A
Cable capacitance	45 to 200 nF/km
Loop resistance	15 to 150 Ω/km
Cable inductance	0.4 to 1 mH/km

Further details are provided in the Ethernet-APL Engineering Guideline (<https://www.ethernet-apl.org>).

Overvoltage protection

Devices without optional overvoltage protection

Equipment from Endress+Hauser fulfills the requirements of the product standard IEC/DIN EN 61326-1 (Table 2 Industrial Environment).

Depending on the type of port (DC power supply, input/output port) different testing levels according to IEC/DIN EN against transient overvoltages are applied (IEC/DIN EN 61000-4-5 Surge):

Test level on DC power ports and input/output ports is 1 000 V line to earth

Overvoltage category

Overvoltage category II

Performance characteristics

Response time	<ul style="list-style-type: none"> ■ HART: <ul style="list-style-type: none"> ■ Acyclic: min. 330 ms, typically 590 ms (depends on commands and number of preambles) ■ Cyclic (burst): min. 160 ms, typically 350 ms (depends on commands and number of preambles) ■ PROFINET with Ethernet-APL: cyclic: min. 32 ms
Reference operating conditions	<ul style="list-style-type: none"> ■ As per IEC 62828-2 ■ Ambient temperature T_A = constant, in the range +22 to +28 °C (+72 to +82 °F) ■ Humidity ϕ = constant, in the range: 5 to 80 % rF \pm 5 % ■ Atmospheric pressure p_U = constant, in the range: 860 to 1 060 mbar (12.47 to 15.37 psi) ■ Position of the measuring cell: horizontal \pm 1° ■ Input of LOW SENSOR TRIM and HIGH SENSOR TRIM for lower range value and upper range value ■ Supply voltage: 24 V DC \pm 3 V DC ■ Load with HART: 250 Ω ■ Turn Down TD= URL/ URV - LRV ■ Zero point-based span
Total performance	<p>The performance characteristics refer to the accuracy of the device. The factors that influence the accuracy can be divided into two groups</p> <ul style="list-style-type: none"> ■ Total performance of device ■ Installation factors <p>All of the performance characteristics meet the requirement of $\geq \pm 3$ sigma.</p> <p>The total performance of the device comprises the reference accuracy and the ambient temperature effect and is calculated using the following formula:</p> $\text{Total performance} = \pm \sqrt{(E1)^2 + (E2)^2}$ <p>E1 = Reference accuracy E2 = Temperature effect</p> <p>Calculation of E2:</p> <p>Temperature effect per ± 28 °C (50 °F) (Corresponds to a range of -3 to $+53$ °C (+27 to +127 °F))</p> $E2 = E2_M + E2_E$ <p>$E2_M$ = Main temperature error $E2_E$ = Electronics error</p> <p>The values refer to the calibrated span.</p> <p>Calculation of the total performance with the Endress+Hauser Applicator</p> <p>Detailed inaccuracies, e.g. for other temperature ranges, can be calculated with the Applicator "Sizing Pressure Performance".</p>



A0038927

Reference accuracy [E1]

The reference accuracy comprises the non-linearity according to the limit point method, pressure hysteresis and non-repeatability in accordance with [IEC62828-1]. Reference accuracy for standard up to TD 100:1, for platinum up to TD 10:1.

Gauge pressure measuring cells

Measuring cell	Standard	Platinum
100 mbar (1.5 psi)	TD 1:1 to 10:1 = $\pm 0.15\%$ TD > 10:1 = $\pm 0.015\% \cdot \text{TD}$	TD 1:1 to 10:1 = $\pm 0.075\%$
250 mbar (3.75 psi)	TD 1:1 to 10:1 = $\pm 0.1\%$ TD > 10:1 = $\pm 0.01\% \cdot \text{TD}$	TD 1:1 to 10:1 = $\pm 0.075\%$
400 mbar (6 psi) 1 bar (15 psi) 2 bar (30 psi) 4 bar (60 psi) 10 bar (150 psi) 40 bar (600 psi)	TD 1:1 to 10:1 = $\pm 0.075\%$ TD > 10:1 = $\pm 0.0075\% \cdot \text{TD}$	TD 1:1 to 10:1 = $\pm 0.055\%$

Absolute pressure measuring cells

Measuring cell	Standard	Platinum
100 mbar (1.5 psi)	TD 1:1 to 10:1 = $\pm 0.15\%$ TD > 10:1 = $\pm 0.015\% \cdot \text{TD}$	TD 1:1 to 10:1 = $\pm 0.075\%$
250 mbar (3.75 psi)	TD 1:1 to 10:1 = $\pm 0.1\%$ TD > 10:1 = $\pm 0.01\% \cdot \text{TD}$	TD 1:1 to 10:1 = $\pm 0.075\%$
400 mbar (6 psi) 1 bar (15 psi) 2 bar (30 psi) 4 bar (60 psi) 10 bar (150 psi) 40 bar (600 psi)	TD 1:1 to 10:1 = $\pm 0.075\%$ TD > 10:1 = $\pm 0.0075\% \cdot \text{TD}$	TD 1:1 to 10:1 = $\pm 0.055\%$

Measuring uncertainty for small absolute pressure measuring ranges

The smallest extended uncertainty of measurement that can be delivered by our standards in the 0.001 to 35 mbar (0.0000145 to 0.5075 psi) range is 0.1 % of the reading + 0.004 mbar (0.000058 psi).

Temperature effect [E2]

$E2_M$ - Main temperature error

The output changes due to the effect of the ambient temperature [IEC 62828-1] with respect to the reference temperature [IEC 62828-1]. The values specify the maximum error due to min./max. ambient or process temperature conditions.

100 mbar (1.5 psi), 250 mbar (3.75 psi) and 400 mbar (6 psi) measuring cell

- Standard: $\pm(0.277\% \cdot \text{TD} + 0.275\%)$
- Platinum: $\pm(0.277\% \cdot \text{TD} + 0.275\%)$

1 bar (15 psi), 2 bar (30 psi), 4 bar (60 psi), 10 bar (150 psi) and 40 bar (600 psi) measuring cell

- Standard: $\pm(0.157\% \cdot \text{TD} + 0.235\%)$
- Platinum: $\pm(0.157\% \cdot \text{TD} + 0.235\%)$

$E2_E$ - Electronics error

- Analog output 4 to 20 mA: 0.2 %
- Digital output HART: 0 %
- Digital output PROFINET: 0 %

Resolution

Current output: <1 μA

Total error

The total error of the device comprises the total performance and the long-term stability effect and is calculated using the following formula:

Total error = total performance + long-term stability

Calculation of the total error with the Endress+Hauser Applicator

Detailed measurement errors, e.g. for other temperature ranges, can be calculated with the Applicator "[Sizing Pressure Performance](#)".



A0038927

Long-term stability

The specifications refer to the upper range limit (URL).

100 mbar (1.5 psi), 250 mbar (3.75 psi), 400 mbar (6 psi) and 1 bar (15 psi) measuring cell

- 1 year: ± 0.20 %
- 5 years: ± 0.40 %
- 10 years: ± 0.50 %


2 bar (30 psi), 4 bar (60 psi), 10 bar (150 psi) and 40 bar (600 psi) measuring cell

- 1 year: ± 0.10 %
- 5 years: ± 0.25 %
- 10 years: ± 0.40 %

Response time T63 and T90

Dead time, time constant

Representation of dead time and time constant as per IEC62828-1:



A0019786

Step response time = dead time (t_1) + time constant T90 (t_3) according to IEC62828-1


Dynamic behavior, current output (analog electronics)

- Dead time (t_1): maximum 50 ms
- Time constant T63 (t_2): maximum 40 ms
- Time constant T90 (t_3): maximum 90 ms

Dynamic behavior, current output (HART electronics)

- Dead time (t_1): maximum 50 ms
- Time constant T63 (t_2): maximum 85 ms
- Time constant T90 (t_3): maximum 200 ms

Installation factors



- A: Axis of membrane horizontal: calibration position, no measurement error
- B: Membrane pointing upwards: measurement error $\leq +0.2$ mbar (+0.003 psi)
- B: Membrane pointing downwards: measurement error ≤ -0.2 mbar (-0.003 psi)



A position-dependent zero point shift can be corrected on the device.

Warm-up time

As per IEC 62828-4: ≤ 5 s

Installation

Orientation

- A position-dependent zero point shift (when the vessel is empty the measured value does not display zero) can be corrected
- The use of shutoff devices and/or siphons is recommended for installation.
- The orientation depends on the measuring application

Installation instructions

- The devices are installed according to the same guidelines as pressure gauges (DIN EN837-2).
- To ensure optimal readability of the local display, align the housing and local display.
- Endress+Hauser offers a mounting bracket for installing the device on pipes or walls.
- Use flushing rings for flanges if there is a risk of medium buildup or clogging at the process connection
 - The flushing ring is clamped between the process connection and process
 - Material buildup in front of the membrane is flushed away and the pressure chamber is vented via the two lateral flushing holes.
- For measurements in media containing solids (e.g. dirty liquids), it makes sense to install separators and drain valves.
- Using a valve allows for easy commissioning, installation and maintenance without interrupting the process.
- When installing the device, establishing the electrical connection and during operation: prevent moisture from entering the housing.
- Point the cable and connector downwards where possible to prevent moisture from entering (e.g. rain or condensation water).

Sensor selection and arrangement

Installing the device

Pressure measurement in gases

Mount the device with the shutoff device above the tapping point so that any condensate can flow into the process.

Pressure measurement in steam

Observe the maximum permitted ambient temperature of the transmitter!

Installation:

- Preferably install the device with a circular siphon below the tapping point.
The device may also be installed above the tapping point.
- Fill the siphon with fluid before commissioning.

Advantages of using siphons:

- Protects the measuring instrument from hot, pressurized media by forming and accumulating condensate
- Dampens pressure shocks
- The defined water column only causes minimal (negligible) measurement errors and minimal (negligible) thermal effects on the device.



For technical data (e.g. materials, dimensions or order numbers), see the accessory document SD01553P.

Pressure measurement in liquids


Mount the device with the shutoff device below or at the same level as the tapping point.

Level measurement

- Always install the device below the lowest measuring point.
- Do not install the device at the following positions:
 - In the filling curtain
 - In the tank outlet
 - In the suction area of a pump
 - At a point in the tank that could be affected by pressure pulses from the agitator
- Install the device downstream from a shutoff device: the functional test and adjustment can then be carried out more easily.

Mounting bracket for device or separate housing

The device or the separate housing can be mounted on walls or pipes (for pipes with a diameter of 1 ¼" to 2") using the mounting bracket.



Unit of measurement mm (in)

Ordering information:

- Can be ordered via the Product Configurator
- Can be ordered as a separate accessory, part number 71102216

 The mounting bracket is included in the delivery if you order the device with a separate housing.

Special mounting instructions

Wall and pipe mounting with a manifold (optional)

If the device is mounted on a shutoff device (e.g. manifold or shutoff valve), then use the bracket provided for this purpose. This makes it easier to disassemble the device.

For technical data, see the SD01553P accessory document.

Sensor, remote (separate housing)

The housing of the device (including electronic insert) is mounted away from the measuring point.


This version thus facilitates trouble-free measurement

- Under particularly difficult measuring conditions (at installation locations that are cramped or difficult to access)
- If the measuring point is exposed to vibrations

Cable versions:

- PE: 2 m (6.6 ft), 5 m (16 ft) and 10 m (33 ft)
- FEP: 5 m (16 ft).

The sensor is supplied with the process connection and cable fitted. The housing (including electronic insert) and a mounting bracket are enclosed as separate units. The cable is provided with a socket at both ends. These sockets are simply connected to the housing (including electronic insert) and the sensor.



A0038412

- 1 Sensor, remote (including electronic insert)
- 2 Mounting bracket provided, suitable for wall mounting or pipe mounting
- 3 Cable, both ends are fitted with a socket
- 4 Process connection adapter
- 5 Process connection with sensor

Ordering information:

- Sensor, remote (including electronic insert), and mounting bracket can be ordered via the Product Configurator
- Mounting bracket can also be ordered as a separate accessory, part number 71102216

Technical data for cable:

- Minimum bending radius: 120 mm (4.72 in)
- Cable extraction force: max. 450 N (101.16 lbf)
- Resistance to UV light

Use in hazardous area:

- Intrinsically safe installations (Ex ia/IS)
- FM/CSA IS: for Div.1 installation only

Reduction of the installation height

If the "Remote sensor" version is used, the installation height of the process connection is reduced compared to the dimensions of the standard version. For dimensions, see "Mechanical construction" section.

Environment

Ambient temperature range	<p>The following values apply up to a process temperature of +85 °C (+185 °F). The permitted ambient temperature is reduced at higher process temperatures.</p> <ul style="list-style-type: none"> Without segment display or graphic display: Standard: -40 to +85 °C (-40 to +185 °F) With segment display or graphic display: -40 to +85 °C (-40 to +185 °F) with limitations in optical properties such as display speed and contrast for example. Can be used without limitations up to -20 to +60 °C (-4 to +140 °F) Segment display: up to -50 to +85 °C (-58 to +185 °F) with restricted operating life and performance Separate housing: -20 to +60 °C (-4 to +140 °F)
	<p>Hazardous area</p> <ul style="list-style-type: none"> For devices for use in hazardous areas, see the Safety Instructions, Installation Drawing or Control Drawing Devices that have the most common explosion protection certificates (e.g. ATEX/ IEC Ex, etc.) can be used in explosive atmospheres up to the ambient temperature.
Storage temperature	<ul style="list-style-type: none"> Without device display: Standard: -40 to +90 °C (-40 to +194 °F) With device display: -40 to +85 °C (-40 to +185 °F) Separate housing: -40 to +60 °C (-40 to +140 °F) <p>With M12 plug, elbowed: -25 to +85 °C (-13 to +185 °F)</p>
Operating altitude	Up to 5 000 m (16 404 ft) above sea level.
Climate class	<p>Class 4K26 (air temperature: -20 to +50 °C (-4 to +122 °F), relative air humidity: 4 to 100 %) in accordance with IEC/EN 60721-3-4.</p> <p>Condensation is possible.</p>
Degree of protection	<p>Test as per IEC 60529 and NEMA 250-2014</p> <p>Housing and process connection</p> <p>IP66/68, TYPE 4X/6P (IP68: (1.83 mH₂O for 24 h))</p> <p>Cable entries</p> <ul style="list-style-type: none"> Gland M20, plastic, IP66/68 TYPE 4X/6P Gland M20, brass nickel plated, IP66/68 TYPE 4X/6P Gland M20, 316L, IP66/68 TYPE 4X/6P Thread M20, IP66/68 TYPE 4X/6P Thread G1/2, IP66/68 TYPE 4X/6P <p>If the G1/2 thread is selected, the device is delivered with an M20 thread as standard and a G1/2 adapter is included with the delivery, along with the corresponding documentation</p> <ul style="list-style-type: none"> Thread NPT1/2, IP66/68 TYPE 4X/6P Dummy plug transport protection: IP22, TYPE 2 HAN7D plug, 90 degrees, IP65 NEMA Type 4X M12 plug <p>When housing is closed and connecting cable is plugged in: IP66/67 NEMA Type 4X When housing is open or connecting cable is not plugged in: IP20, NEMA Type 1</p> <p>NOTICE</p> <p>M12 plug and HAN7D plug: incorrect installation can invalidate the IP protection class!</p> <ul style="list-style-type: none"> The degree of protection only applies if the connecting cable used is plugged in and screwed tight. The degree of protection only applies if the connecting cable used is specified according to IP67 NEMA Type 4X. The IP protection classes are only maintained if the dummy cap is used or the cable is connected.

Process connection and process adapter when using the separate housing*FEP cable*

- IP69 (on sensor side)
- IP66 TYPE 4/6P
- IP68 (1.83 mH₂O for 24 h) TYPE 4/6P

PE cable

- IP66 TYPE 4/6P
- IP68 (1.83 mH₂O for 24 h) TYPE 4/6P

Vibration resistance**Aluminum single-compartment housing**

Description	Sinusoidal vibration IEC62828-1	Shock
Device	10 Hz to 60 Hz: ±0.35 mm (0.0138 in) 60 Hz to 1000 Hz: 5 g	30 g
Device with Ex d and XP version ¹⁾	10 Hz to 60 Hz: ±0.15 mm (0.0059 in) 60 Hz to 1000 Hz: 2 g	30 g

1) Not for the high-temperature version with Ex d and XP.

Aluminum dual-compartment housing

Description	Sinusoidal vibration IEC62828-1	Shock
Device	10 Hz to 60 Hz: ±0.15 mm (0.0059 in) 60 Hz to 1000 Hz: 2 g	30 g
Device with Ex d version ¹⁾	10 Hz to 60 Hz: ±0.15 mm (0.0059 in) 60 Hz to 1000 Hz: 2 g	30 g

1) Not for the high-temperature version with Ex d and XP.

Electromagnetic compatibility (EMC)

- Electromagnetic compatibility as per IEC 61326 series and NAMUR recommendation EMC (NE21)
- With regard to the safety function (SIL), the requirements of IEC 61326-3-x are satisfied.
- Maximum deviation with interference influence: < 0.5% of span with full measuring range (TD 1:1)

For more details refer to the EU Declaration of Conformity.

Process


Process temperature range

NOTICE

The permitted process temperature depends on the process connection, process seal, ambient temperature and the type of approval.

- ▶ All the temperature data in this document must be taken into consideration when selecting the device.

–40 to +100 °C (–40 to +212 °F)



A0043294

6 Values apply for vertical mounting without insulation.

T_p Process temperature

T_a Ambient temperature

The process temperature ranges indicated refer to the permanent operation of the device (maximum 5 °C (41 °F) deviation is permitted)

Seals

Pay attention to the process temperature range of the seal. The temperatures indicated depend on the resistance of the seal to the medium.

Seal	Temperature
FKM	–25 to +100 °C (–13 to +212 °F)
FKM Cleaned for oxygen service	–10 to +60 °C (+14 to +140 °F)
FFKM Perlast G75LT	–20 to +100 °C (–4 to +212 °F)
FFKM Kalrez 6375	+5 to +100 °C (+41 to +212 °F)
FFKM Chemraz 505	–10 to +100 °C (+14 to +212 °F)
EPDM	–40 to +100 °C (–40 to +212 °F)
HNBR	–25 to +100 °C (–13 to +212 °F)

Oxygen applications (gaseous)

Oxygen and other gases can react explosively to oils, grease and plastics. The following precautions must be taken:

- All components of the system, such as devices, must be cleaned in accordance with national requirements.
- Depending on the materials used, a certain maximum temperature and a maximum pressure must not be exceeded for oxygen applications.

The cleaning of the device (not accessories) is provided as an optional service.

Devices with measuring cells, nominal value < 10 bar (150 psi)

T_{\max}	P_{\max}
60 °C (140 °F)	Overpressure limit (OPL) of the measuring cell and depending on the process connection used
Devices with PVDF threads ¹⁾ : 60 °C (140 °F)	15 bar (225 psi)

1) Only mount with the enclosed mounting bracket!

Devices with measuring cells, nominal value ≥ 10 bar (150 psi)

T_{\max}	P_{\max}
60 °C (140 °F)	40 bar (600 psi)

Thermal shock

Applications with jumps in temperature

Extreme jumps in temperature can result in temporary measuring errors. Temperature compensation takes place after a few minutes. Internal temperature compensation is faster the smaller the jump in temperature and the longer the time interval involved.



For more information: contact the Endress+Hauser sales office.

Process pressure range

Pressure specifications



The maximum pressure for the device depends on the lowest-rated element with regard to pressure.

Components are: process connection, optional mounting parts, or accessories.

⚠ WARNING

Incorrect design or use of the device may cause injury due to bursting parts!

- ▶ Only operate the device within the specified limits for the components!
- ▶ MWP (maximum working pressure): The maximum working pressure is specified on the nameplate. This value refers to a reference temperature of +20 °C (+68 °F) and may be applied to the device for an unlimited time. Note temperature dependence of MWP. For flanges, refer to the following standards for the permitted pressure values at higher temperatures: EN 1092-1 (with regard to their stability/temperature property, the materials 1.4435 and 1.4404 are grouped together under EN 1092-1; the chemical composition of the two materials can be identical.), ASME B 16.5a, JIS B 2220 (the latest version of the standard applies in each case). Maximum working pressure data that deviate from this are provided in the relevant sections of the Technical Information.
- ▶ The overpressure limit is the maximum pressure that a device may be subjected to during a test. The overpressure limit exceeds the maximum working pressure by a certain factor. This value refers to a reference temperature of +20 °C (+68 °F).
- ▶ The Pressure Equipment Directive (2014/68/EU) uses the abbreviation "PS". The abbreviation "PS" corresponds to the MWP (maximum working pressure) of the device.
- ▶ The Pressure Equipment Directive (2014/68/EU) uses the abbreviation "PT". The abbreviation "PT" corresponds to the OPL (Over Pressure Limit) of the device. OPL (Over Pressure Limit) is a test pressure.
- ▶ In the case of measuring cell range and process connection combinations where the overpressure limit (OPL) of the process connection is less than the nominal value of the measuring cell, the device is set at the factory, at the very maximum, to the OPL value of the process connection. If the entire measuring cell range must be used, select a process connection with a higher OPL value (1.5 x PN; MWP = PN).
- ▶ Oxygen applications: do not exceed values for P_{\max} and T_{\max} .

Burst pressure

As of the specified burst pressure, the complete destruction of the pressure-bearing parts and/or a device leak must be expected. It is therefore imperative to avoid such operating conditions by carefully planning and sizing your facility.

Ultrapure gas applications	Endress+Hauser also offers devices for special applications, such as for ultrapure gas, that are cleaned of oil and grease. No special restrictions regarding the process conditions apply to these devices.
Steam applications and saturated steam applications	For steam and saturated steam applications: Use a device with a metallic membrane or provide a siphon for temperature decoupling when installing.

Mechanical construction


Design dimensions

Device height

The device height is calculated from

- the height of the housing
- the height of the individual process connection

The individual heights of the components are listed in the following sections. To calculate the device height, add the individual heights of the components. Take the installation clearance into consideration (space that is used to install the device).




A0043569

- A* Installation clearance
B Height of the housing
H Height of the process connection

Dimensions

Single-compartment housing



A0054983


Unit of measurement mm (in)

- 1 Device with display, cover with sight glass made of glass (devices for Ex d/XP, dust Ex): 138 mm (5.43 in)
- 2 Device with display, cover with plastic sight glass: 127 mm (5 in)
- 3 Device without display, cover without sight glass: 124 mm (4.88 in)



Cover optionally with ANSI Safety Red (color RAL3002) coating.

Dual-compartment housing



A0038377


Unit of measurement mm (in)

- 1 Device with display, cover with sight glass made of glass (devices for Ex d/XP, dust Ex): 132 mm (5.2 in)
- 2 Device with display, cover with plastic sight glass: 121 mm (4.76 in)
- 3 Device without display, cover without sight glass: 118 mm (4.65 in)



Cover optionally with ANSI Safety Red (color RAL3002) coating.

Stainless steel dual-compartment housing, precision cast




A0058028


Unit of measurement mm (in)

- 1 Device with display, cover with sight glass made of glass (devices for Ex d/XP, dust Ex): 136 mm (5.35 in)
- 2 Device without display, cover without sight glass: 133 mm (5.24 in)

Sensor, remote (separate housing)



A0058871

Bracket and cable length

A0038214

Unit of measurement mm (in)

1 86 mm (3.39 in)

L Length of cable versions

Maximum working pressure and overpressure limit

The maximum working pressure (MWP) and the overpressure limit (OPL) of the sensor can deviate from the maximum MWP and OPL of the process connection.

Explanation of terms

- DN or NPS or A = alphanumeric identifier of the flange size
- PN or Class or K = alphanumeric pressure rating of a component

Outer diameter of capillary

Designation	Outer diameter
Flexible armor made from 316L	8 mm (0.31 in)
Flexible armor with PVC-coating	10 mm (0.39 in)
Flexible armor with PTFE-coating	12.5 mm (0.49 in)

Height H

Process connection	Height H	
	Standard	Ex d version
FNPT1/2 MNPT1/2 MNPT1/2 FNPT1/4 G1/2 M20x1.5 B0202 B0203	28 mm (1.1 in)	94 mm (3.7 in)
MNPT1-1/2 MNPT2 G1-1/2 G2 M44x1.25	59 mm (2.32 in)	125 mm (4.92 in)
Flanges	83 mm (3.27 in)	150 mm (5.91 in)

Thread ISO228 G, internal membrane

<p>A</p> <p>ø8 (0.31) ø3 (0.12) ø6 (0.24) G 1/2" 17 (0.67) 20 (0.79) 3 (0.12) H</p> <p>A0020935</p>	<p>B</p> <p>G 1/4" ø17.5 (0.24) G 1/2" 13 (0.51) 17 (0.67) 20 (0.79) H</p> <p>A0020936</p>
<p>C</p> <p>ø11.4 (0.45) ø17.5 (0.24) G 1/2" 17 (0.67) 20 (0.79) H</p> <p>A0020937</p>	
Unit mm (in)	

Position	Description	Material	Order option ¹⁾
A	Thread ISO228 G 1/2" A EN837	AISI 316L	WBJ
		Alloy C276 (2.4819)	WBC
		PVDF <ul style="list-style-type: none"> Only mount with a mounting bracket (included) MWP 10 bar (150 psi), OPL max. 15 bar (225 psi) Process temperature range: -10 to +60 °C (+14 to +140 °F) 	WBE
B	Thread ISO228 G 1/2" A, G 1/4" (female)	AISI 316L	WXJ
		Alloy C276 (2.4819)	WXC
C	Thread ISO228 G 1/2" A, Bore 11.4 mm (0.45 in)	AISI 316L	WWJ
		Alloy C276 (2.4819)	WWC

1) Product Configurator order code for "Process connection"

Thread ASME B1.20.1, NPT, internal membrane


<p>A</p> <p>NPT 1/4"</p> <p>NPT 1/2"</p> <p>25 (0.98)</p> <p>A0020938</p>	<p>B</p> <p>ø11.4 (0.45)</p> <p>NPT 1/2"</p> <p>25 (0.98)</p> <p>A0020939</p>
<p>C</p> <p>ø3 (0.12)</p> <p>NPT 1/2"</p> <p>25 (0.98)</p> <p>A0020940</p>	<p>D</p> <p>NPT 1/2"</p> <p>ø26.5 (1.04)</p> <p>25 (0.98)</p> <p>A0020943</p>
<p>Unit mm (in)</p>	

Position	Description	Material	Order option ¹⁾
A ²⁾	Thread ASME MNPT 1/2", FNPT 1/4"	AISI 316L	VXJ
		Alloy C276 (2.4819)	VXC
B	Thread ASME MNPT 1/2", Bore 11.4 mm (0.45 in)	AISI 316L	VWJ
		Alloy C276 (2.4819)	VWC
C	Thread ASME MNPT 1/2", Bore 3 mm (0.12 in)	PVDF <ul style="list-style-type: none"> Only mount with a mounting bracket (included) MWP 10 bar (150 psi), OPL max. 15 bar (225 psi) Process temperature range: -10 to +60 °C (+14 to +140 °F) 	VVE
D	Thread ASME FNPT 1/2"	AISI 316L	VNJ
		Alloy C276 (2.4819)	VNC

1) Product Configurator order code for "Process connection"

2) URL max. 100 bar (1 500 psi)


Thread JIS, internal membrane



Position	Description	Material	Order option ¹⁾
A	JIS B0202 G 1/2" (male)	AISI 316L	ZBJ
B	JIS B0203 R 1/2" (male)		ZJJ

1) Product Configurator order code for "Process connection"


Thread, metric (DIN 13), internal membrane



Position	Description	Material	Order option ¹⁾
A	DIN 13 M20 x 1.5, 3 mm (0.12 in)	AISI 316L	XZJ
		Alloy C276 (2.4819)	XZC

1) Product Configurator order code for "Process connection"


Thread ISO 228 G, flush membrane



Item	Designation	Material	Order option ¹⁾		
A	Thread ISO 228 G 1 1/2" A	AISI 316L	WNJ		
		B	Thread ISO 228 G 2" A	AISI 316L	WPJ

1) Product Configurator order code for "Process connection"


Thread ASME, NPT, flush membrane



Position	Description	Material	Order option ¹⁾
A	Thread ASME 1 1/2" MNPT	AISI 316L	VLJ
B	Thread ASME 2" MNPT	AISI 316L	VMJ

1) Product Configurator order code for "Process connection"

Thread DIN 13, flush membrane




Description	Material	Order option ¹⁾
DIN 13 M44 x 1.25	AISI 316L	X7J
	Alloy C276 (2.4819)	X7C

1) Product Configurator order code for "Process connection"

Flange EN1092-1, flush membrane

Connection dimensions according to EN1092-1.



A0020955

D Diameter of flange
b Thickness
g Raised face
k Pitch diameter
g₂ Diameter of hole

Unit mm

Flange							Boltholes			Order option ¹⁾
Material	DN	PN	Form	D	b	g	Number	g ₂	k	
				mm	mm	mm		mm	mm	
AISI 316L	DN 25	PN 10-40	B1	115	18	68	4	14	85	H0J
AISI 316L	DN 32	PN 10-40	B1	140	18	78	4	18	100	H1J
AISI 316L	DN 40	PN 10-40	B1	150	18	88	4	18	110	H2J
PVDF ²⁾ ³⁾	DN 40	PN 10-16	B2	150	21.4	88	4	18	110	EPE
ETFE ³⁾	DN 40	PN 10-40	B2	150	21	88	4	18	110	H2N
AISI 316L	DN 50	PN 10-40	B1	165	20	102	4	18	125	H3J
PVDF ²⁾ ³⁾	DN 50	PN 10-16	B2	165	21.4	102	4	18	125	EQE
ETFE ³⁾	DN 50	PN 25-40	B2	165	21	102	4	18	125	E2N
AISI 316L	DN 80	PN 10-40	B1	200	24	138	8	18	160	H5J
ETFE ³⁾	DN 80	PN 25-40	B2	200	25	138	8	18	160	E4N


1) Product Configurator order code for "Process connection"

2) MWP 10 bar (150 psi), OPL max. 15 bar (225 psi); process temperature range: -10 to +60 °C (+14 to +140 °F)

3) ETFE coating on AISI 316L (1.4404). When operating in hazardous areas, avoid electrostatic charging of the plastic surfaces.

Flange ASME B16.5, RF, flush membrane

Connection dimensions in accordance with ASME B16.5, raised face RF



A0034685

D Diameter of flange
b Thickness
g Raised face
k Pitch diameter
g₂ Diameter of hole


Unit in

Flange						Boltholes			Order option ¹⁾
Material	NPS	Class	D	b	g	Number	g ₂	k	
	in		in	in	in		in	in	
AISI 316/316L ^{2) 3)}	1	150	4.25	1.18	2	4	0.62	3.12	AAJ
AISI 316/316L ^{2) 3)}	1	300	4.88	1.18	2	4	0.75	3.5	AMJ
AISI 316/316L ²⁾	1 ½	150	5	0.69	2.88	4	0.62	3.88	ACJ
AISI 316/316L ²⁾	1 ½	300	6.12	0.81	2.88	4	0.88	4.5	APJ
AISI 316/316L ²⁾	2	150	6	0.75	3.62	4	0.75	4.75	ADJ
ETFE ⁴⁾	2	150	6	0.75	3.62	4	0.75	4.75	ADN
AISI 316/316L ²⁾	2	300	6.5	0.88	3.62	8	0.75	5	AQJ
AISI 316/316L ²⁾	3	150	7.5	0.94	5	4	0.75	6	AFJ
ETFE ⁴⁾	3	150	7.5	0.94	5	4	0.75	6	AFN
PVDF ⁵⁾	3	150	7.5	0.94	5	4	0.75	6	AFE
AISI 316/316L ²⁾	3	300	8.25	1.12	5	8	0.88	6.62	ASJ
AISI 316/316L ²⁾	4	150	9	0.94	6.19	8	0.75	7.5	AGJ
ETFE ⁴⁾	4	150	9	0.94	6.19	8	0.75	7.5	AGN
AISI 316/316L ²⁾	4	300	10	1.25	6.19	8	0.88	7.88	ATJ

- 1) Product Configurator order code for "Process connection"
- 2) Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual rated)
- 3) Screws must be 15 mm (0.59 in) longer than the standard flange screws
- 4) ETFE coating on AISI 316/316L. When operating in hazardous areas, avoid electrostatic charging of the plastic surfaces.
- 5) MWP 10 bar (150 psi), OPL max. 15 bar (225 psi); process temperature range: -10 to +60 °C (+14 to +140 °F)

Flange JIS B2220, RF, flush membrane

Connection dimensions in accordance with JIS B 2220 BL, raised face RF



A0034684

D Diameter of flange
b Thickness
g Raised face
k Pitch diameter
g₂ Diameter of hole

Unit mm

Flange						Boltholes			Order option ¹⁾
Material	A ²⁾	K ³⁾	D	b	g	Number	g ₂	k	
			mm	mm	mm		mm	mm	
AISI 316L (1.4435)	40 A	10 K	140	16	81	4	19	105	PCJ
	50 A	10 K	155	16	96	4	19	120	PDJ
	80 A	10 K	185	18	127	8	19	150	PFJ
	100 A	10 K	210	18	151	8	19	175	PGJ

1) Product Configurator order code for "Process connection"

2) Alphanumeric designation of the flange size.

3) Alphanumeric pressure rating of a component.

Weight

Housing

Weight including electronics and display.

- Single-compartment housing: 1.1 kg (2.43 lb)
- Dual-compartment housing
Aluminum: 1.4 kg (3.09 lb)

Sensor, remote (separate housing)

- Housing: see the Housing section
- Housing adapter: 0.55 kg (1.21 lb)
- Process connection adapter: 0.36 kg (0.79 lb))
- Cable:
 - PE cable, 2 meters: 0.18 kg (0.40 lb)
 - PE cable, 5 meters: 0.35 kg (0.77 lb)
 - PE cable, 10 meters: 0.64 kg (1.41 lb)
 - FEP cable, 5 meters: 0.62 kg (1.37 lb)
- Mounting bracket: 0.46 kg (1.01 lb)

Process connections

Threaded connection		Flanges	
Weight ¹⁾	Order option ²⁾	Weight ¹⁾	Order option ²⁾
0.80 kg (1.76 lb)	VLJ	2.30 kg (5.07 lb)	AAJ
1.20 kg (2.65 lb)	VMJ	8.50 kg (18.74 lb)	AMJ

Threaded connection		Flanges	
Weight ¹⁾	Order option ²⁾	Weight ¹⁾	Order option ²⁾
0.60 kg (1.32 lb)	VNC	2.10 kg (4.63 lb)	ACJ
0.60 kg (1.32 lb)	VNJ	3.30 kg (7.28 lb)	APJ
0.60 kg (1.32 lb)	VXC	3.10 kg (6.84 lb)	ADJ
0.60 kg (1.32 lb)	VVE	3.10 kg (6.84 lb)	ADN
0.60 kg (1.32 lb)	VWC	4.00 kg (8.82 lb)	AQJ
0.60 kg (1.32 lb)	VWJ	5.70 kg (12.57 lb)	AFJ
0.60 kg (1.32 lb)	VXJ	5.70 kg (12.57 lb)	AFN
0.60 kg (1.32 lb)	WBC	1.60 kg (3.53 lb)	AFE
0.60 kg (1.32 lb)	WBE	7.5 kg (16.54 lb)	ASJ
0.60 kg (1.32 lb)	WBJ	7.60 kg (16.76 lb)	AGJ
0.60 kg (1.32 lb)	WXC	7.80 kg (17.20 lb)	AGN
0.60 kg (1.32 lb)	WXJ	12.40 kg (27.34 lb)	ATJ
0.60 kg (1.32 lb)	WWJ	3.70 kg (8.16 lb)	E2N
0.60 kg (1.32 lb)	WWC	5.20 kg (11.47 lb)	E4N
0.8 (1.76)	WNJ	1.30 kg (2.87 lb)	EPE
1.2 (2.65)	WPJ	1.40 kg (3.09 lb)	EQE
0.90 (1.98)	X7C	1.90 kg (4.19 lb)	H0J
0.90 (1.98)	X7J	2.50 kg (5.51 lb)	H1J
0.60 (1.32)	XZC	3.00 kg (6.62 lb)	H2J
0.60 (1.32)	XZJ	3.50 kg (7.72 lb)	H3J
0.60 (1.32)	ZBJ	5.80 kg (12.79 lb)	H5J
0.60 (1.32)	ZJJ	3.00 kg (6.62 lb)	H2N
-	-	2.90 kg (6.39 lb)	PDJ
-	-	3.90 kg (8.60 lb)	PFJ
-	-	5.30 kg (11.69 lb)	PGJ
-	-	2.50 kg (5.51 lb)	PCJ

- 1) Total weight consisting of sensor assembly and process connection.
2) Product Configurator order code for "Process connection"

Accessories

Mounting bracket: 0.5 kg (1.10 lb)

Materials in contact with process

Membrane material

Al₂O₃ aluminum oxide ceramic, ultrapure 99.9%, Ceraphire® (see also www.endress.com)

Seal

- FKM
- EPDM (FDA 21 CFR 177.2600)
- HNBR (FDA 21 CFR 177.2600)
- FFKM Perlast G75LT
- FFKM Chemraz 505
- FFKM Kalrez 6375

Process connections

See the specific process connection.

Accessories



For technical data (e.g. materials, dimensions or order numbers), see the accessory document SD01553P.

Materials not in contact with process

Single compartment housing, aluminum, coated

- Housing: EN AC-43400 aluminum
- Housing coating, cover: polyester
- EN AC-43400 aluminum cover with Lexan 943A PC sight glass
- EN AC-443400 aluminum cover with borosilicate sight glass; dust-Ex for Ex d/XP
- Dummy cover: EN AC-43400 aluminum
- Cover sealing materials: HNBR
- Cover sealing materials: FVMQ (in low temperature version only)
- Plug: PBT-GF30-FR or aluminum
- Plug sealing material: EPDM
- Nameplate: plastic foil
- TAG plate: plastic foil, stainless steel or provided by the customer



The cable entry with material specification can be ordered via the product structure "Electrical connection".

Dual compartment housing, aluminum, coated

- Housing: EN AC-43400 aluminum
- Housing coating, cover: polyester
- EN AC-43400 aluminum cover with Lexan 943A PC sight glass
- EN AC-443400 aluminum cover with borosilicate sight glass; dust-Ex for Ex d/XP
- Dummy cover: EN AC-43400 aluminum
- Cover sealing materials: HNBR
- Cover sealing materials: FVMQ (in low temperature version only)
- Plug: PBT-GF30-FR or aluminum
- Plug sealing material: EPDM
- Nameplate: plastic foil
- TAG plate: plastic foil, stainless steel or provided by the customer



The cable entry with material specification can be ordered via the product structure "Electrical connection".

Electrical connection

Coupling M20, plastic

- Material: PA
- Seal on cable gland: EPDM
- Dummy plug: plastic

Coupling M20, nickel-plated brass

- Material: nickel-plated brass
- Seal on cable gland: EPDM
- Dummy plug: plastic

Coupling M20, 316L

- Material: 316L
- Seal on cable gland: EPDM
- Dummy plug: plastic

M20 coupling, 316 L, hygiene

- Material: 316L
- Seal on cable gland: EPDM

M20 thread

The device is supplied with M20 thread as standard.

Transport plug: LD-PE

Thread G ½

The device is supplied as standard with an M20 thread and an enclosed adapter to G ½ including documentation (aluminum housing, 316L housing, hygienic housing) or with a mounted adapter to G ½ (plastic housing).

- Adapter made of PA66-GF or aluminum or 316L (depends on housing version ordered)
- Transport plug: LD-PE

NPT ½ thread

The device is supplied as standard with an NPT ½ thread (aluminum housing, 316L housing) or with a mounted adapter to NPT ½ (plastic housing, hygienic housing).

- Adapter made of PA66-GF or 316L (depends on housing version ordered)
- Transport plug: LD-PE

Thread NPT ¾

The device is supplied with NPT ¾ thread as standard.

Transport plug: LD-PE

M20 coupling, blue plastic

- Material: PA, blue
- Seal on cable gland: EPDM
- Dummy plug: plastic

M12 plug

- Material: nickel-plated CuZn or 316L (depends on housing version ordered)
- Transport cap: LD-PE

HAN7D plug

Material: aluminum, die-cast zinc, steel

Valve plug ISO44000 M16

- Material: PA6
- Transport plug: LD-PE

Separate housing

- Mounting bracket
 - Bracket: AISI 316L (1.4404)
 - Screw and nuts: A4-70
 - Half-shells: AISI 316L (1.4404)
- Seal for cable from separate housing: EPDM
- Gland for cable of separate housing: AISI 316L (1.4404)
- PE cable for separate housing: abrasion-proof cable with strain-relief Dynema members; shielded using aluminum-coated foil; insulated with polyethylene (PE-LD), black; copper wires, twisted, UV-resistant
- FEP cable for separate housing: abrasion-proof cable; shielded using galvanized steel wire netting; insulated with fluorinated ethylene propylene (FEP), black; copper cores, twisted, UV-resistant
- Process connection adapter for separate housing: AISI 316L (1.4404)

Connecting parts

- Connection between housing and process connection: AISI 316L (1.4404)
- Measuring cell body: AISI 316L (1.4404)

Accessories



For technical data (e.g. materials, dimensions or order numbers), see the accessory document SD01553P.

Operability

Operating concept (not for devices with 4 to 20 mA analog)

Operator-oriented menu structure for user-specific tasks

- Guidance
- Diagnostics
- Application
- System

Quick and safe commissioning

- Interactive wizard with graphical user interface for guided commissioning in FieldCare, DeviceCare or DTM, AMS and PDM-based third-party tools or SmartBlue
- Menu guidance with brief explanations of the individual parameter functions
- Standardized operation at the device and in the operating tools
- PROFINET over Ethernet-APL: access to the device via web server

Efficient diagnostic behavior increases measurement reliability

- Remedial action is integrated in plain text
- Various simulation options


Bluetooth module (optionally integrated in local display)

- Quick and easy setup with SmartBlue app or PC with DeviceCare, version 1.07.00 and higher, or FieldXpert SMT70
- No additional tools or adapters needed
- Encrypted single point-to-point data transmission (tested by Fraunhofer Institute) and password-protected communication via *Bluetooth®* wireless technology

Local operation

Operating keys and DIP switches on the electronic insert


Analog 4 to 20 mA



A0039344

- 1 Operating key for lower range value (Zero)
- 2 Operating key for upper range value (Span)
- 3 DIP switch for damping
- 4 DIP switch for locking and unlocking the device

HART




A0039285

- 1 Operating key for lower range value (Zero)
- 2 Operating key for upper range value (Span)
- 3 DIP switch for alarm current
- 4 DIP switch for locking and unlocking the device



The setting of the DIP switches has priority over the settings made via other operation methods (e.g. FieldCare/DeviceCare).

PROFINET with Ethernet-APL



A0046061

- 1 Operating key for position adjustment (zero point correction) and device reset
- 2 DIP switch for setting the service IP address
- 3 DIP switch for locking and unlocking the device

i The setting of the DIP switches has priority over the settings made via other operation methods (e.g. FieldCare/DeviceCare).


Local display

Device display (optional)

Functions:

- Display measured values and fault and notice messages
- The device display can be removed for easier operation


i The device displays are available with the additional option of Bluetooth® wireless technology.



A0047140

7 Segment display

- 1 Measured value (up to 5 digits)
- 2 Bar graph (refers to the specified pressure range) proportional to current output
- 3 Unit of measured value
- 4 Locking (symbol appears when device is locked)
- 5 Measured value output in %




A0043599

8 Segment display

- 1 Measured value (up to 5 digits)
- 2 Bar graph (refers to the specified pressure range) proportional to the current output (not for PROFINET over Ethernet-APL or PROFIBUS PA)
- 3 Unit of measured value
- 4 Locking (symbol appears when device is locked)
- 5 Bluetooth (symbol flashes if Bluetooth connection is active)
- 6 HART communication, PROFINET over Ethernet-APL communication or PROFIBUS PA communication (symbol appears when communication is enabled)
- 7 Measured value output in %

Remote operation

Via HART protocol or Bluetooth




A0044334

9 Options for remote operation via HART protocol

- 1 PLC (programmable logic controller)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and AMS Trex™ device communicator
- 4 AMS Trex™ device communicator
- 5 Computer with operating tool (e.g. DeviceCare/FieldCare, AMS Device View, SIMATIC PDM)
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SMT70/SMT77, smartphone or computer with operating tool (e.g. DeviceCare/FieldCare, AMS Device View, SIMATIC PDM)
- 8 Bluetooth modem with connecting cable (e.g. VIATOR)
- 9 Transmitter

Via PROFINET over Ethernet-APL network




10 Options for remote operation via PROFINET over Ethernet-APL network: star topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch
- 3 Computer with web browser (e.g., Microsoft Edge) for accessing the integrated device web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with iDTM PROFINET Communication
- 4 APL power switch (optional)
- 5 APL field switch
- 6 APL field device

Call up the website via the computer in the network. The IP address of the device must be known.

The IP address can be assigned to the device in a variety of ways:

- Dynamic Configuration Protocol (DHCP), factory setting
The automation system (e.g. Siemens S7) automatically assigns the IP address to the device.
- Software addressing
The IP address is entered via the IP address parameter.
- .DIP switch for service
The device then has the fixed IP address 192.168.1.212.
 The IP address is only adopted following a restart.
The IP address can now be used to establish the connection to the network.

The default setting is that the device uses the Dynamic Configuration Protocol (DHCP). The automation system (e.g. Siemens S7) automatically assigns the IP address of the device.

Via Web browser (for devices with PROFINET)

Function scope

Thanks to the integrated Web server the device can be operated and configured via a Web browser. The structure of the operating menu is the same as for the local display. In addition to the measured values, device status information is also displayed and allows users to monitor the status of the device. Furthermore the device data can be managed and the network parameters can be configured.

Via service interface (CDI)

With the Commubox FXA291, a CDI connection is established with the device interface and a Windows PC/notebook with a USB port.

Operation via Bluetooth® wireless technology (optional)

Prerequisite

- Device with Bluetooth display
- Smartphone or tablet with Endress+Hauser SmartBlue app or PC with DeviceCare from version 1.07.00 or FieldXpert SMT70

The connection has a range of up to 25 m (82 ft). The range can vary depending on environmental conditions such as attachments, walls or ceilings.

System integration

HART

Version 7

PROFINET over Ethernet-APL

PROFINET Profile 4.02

Supported operating tools


Smartphone or tablet with Endress+Hauser SmartBlue (app), DeviceCare, version 1.07.00 and higher, FieldCare, DTM, AMS and PDM.

PC with Web server via fieldbus protocol.

Certificates and approvals

Current certificates and approvals for the product are available at www.endress.com on the relevant product page:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Downloads**.

CE mark	The device meets the legal requirements of the relevant EC directives. Endress+Hauser confirms that the device has been successfully tested by applying the CE mark.
RCM-Tick marking	<p>The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products bear the RCM-Tick marking on the nameplate.</p> <div style="text-align: center;">  </div> <p style="text-align: right; font-size: small;">A0029561</p>
Ex approvals	<ul style="list-style-type: none"> ■ ATEX ■ CSA ■ NEPSI ■ UKCA ■ INMETRO ■ KC ■ EAC ■ JPN ■ Combinations of different approvals also <p>All the data related to explosion protection is provided in separate Ex documentation which is also available upon request. The Ex documentation is supplied as standard with all devices approved for use in explosion hazardous areas.</p> <p>Additional approvals in preparation.</p> <p>Explosion-protected smartphones and tablets</p> <p>If used in hazardous areas, mobile end devices with an Ex approval must be used.</p>
Sanitary compatibility	<p>The following applies for the ceramic membrane:</p> <p>The US Food & Drug Administration (FDA) has no objections to the use of ceramics made from aluminum oxide as a surface material in contact with foodstuffs. This declaration is based on the FDA certificates of our ceramic suppliers.</p>
EAC conformity	<p>The device meets the legal requirements of the applicable EAC Directives. These are listed in the corresponding EAC Declaration of Conformity along with the standards applied.</p> <p>Endress+Hauser confirms successful testing of the device by affixing to it the EAC mark.</p>
Drinking water approval	<ul style="list-style-type: none"> ■ NSF/ANSI 61 drinking water approval ■ KTW drinking water approval W 270
Overfill protection system	The device is tested in accordance with the approval guidelines for overfill protection units (ZG-ÜS:2012-07) as overfill protection as per Section 63 of the German Water Resources Act (WHG).
Functional safety SIL/ IEC 61508 Declaration of Conformity	The devices with a 4-20 mA output signal have been developed according to the IEC 61508 standard. These devices can be used to monitor the process level and pressure up to SIL 3. For a detailed description of the safety functions, settings and functional safety data, see the "Functional Safety Manual".

Marine approval	<ul style="list-style-type: none"> ■ ABS (American Bureau of Shipping) ■ LR (Lloyd's Register) ■ BV (Bureau Veritas) ■ DNV GL (Det Norske Veritas / German Lloyd)
Radio approval	Displays with Bluetooth LE have radio licenses according to CE and FCC. The relevant certification information and labels are provided on display.
CRN approval	A CRN approval (Canadian Registration Number) is available for some device versions. These devices are fitted with a separate plate bearing the registration number CRN 0F23358.5C. In order to obtain a CRN-approved device, a CRN-approved process connection must be ordered along with the option "CRN" in the order code for "Additional approvals".
Test reports	<p>Test, certificate, declarations</p> <ul style="list-style-type: none"> ■ Inspection certificate 3.1, EN10204 (material certificate, wetted metallic parts) The selection of this feature for coated process membranes/process connections refers to the metallic base material. ■ NACE MR0175 / ISO 15156 (wetted metallic parts), declaration ■ NACE MR0103 / ISO 17945 (wetted metallic parts), declaration ■ AD 2000 (wetted metal parts), declaration, excluding membrane ■ Pressure test, internal procedure, test report ■ Helium leak test, internal procedure, test report ■ PMI test, internal procedure (wetted metallic parts), test report <p>All test reports, declarations and inspection certificates are provided electronically in the Device Viewer: Enter the serial number of the nameplate (https://www.endress.com/de/pages/supporting-tools/device-viewer).</p> <p>Applicable for the order codes "Calibration" and "Test, certificate".</p> <p>Product documentation on paper</p> <p>Test reports, declarations and inspection certificates in hard copy can optionally be ordered with the order option "Product documentation on paper". These documents are supplied with the ordered product.</p> <p>Calibration</p> <p>5-point calibration certificate</p> <p>10-point calibration certificate, traceable to ISO/IEC 17025</p> <p>Manufacturer declarations</p> <p>Various manufacturer declarations can be downloaded from the Endress+Hauser website. Other manufacturer declarations can be ordered from the Endress+Hauser sales office.</p> <p><i>Downloading the Declaration of Conformity</i></p> <p>www.endress.com → Download</p>
Pressure Equipment Directive 2014/68/EU (PED)	<p>Pressure equipment with permitted pressure ≤ 200 bar (2 900 psi)</p> <p>Pressure equipment (maximum working pressure $PS \leq 200$ bar (2 900 psi)) can be classified as pressure accessories in accordance with Pressure Equipment Directive 2014/68/EU. If the maximum working pressure is ≤ 200 bar (2 900 psi) and the pressurized volume of the pressure equipment is ≤ 0.1 l, the pressure equipment is subject to the Pressure Equipment Directive (see Pressure Equipment Directive 2014/68/EU, Article 4, point 3). The Pressure Equipment Directive only requires that the pressure equipment shall be designed and manufactured in accordance with the "sound engineering practice of a Member State".</p> <p><i>Reasons:</i></p> <ul style="list-style-type: none"> ■ Pressure Equipment Directive (PED) 2014/68/EU Article 4, point 3 ■ Pressure Equipment Directive 2014/68/EU, Commission's Working Group "Pressure", Guideline A-05 + A-06

Note:

A partial examination shall be performed for pressure instruments that are part of a safety instrumented system for the protection of a pipe or vessel from exceeding allowable limits (equipment with safety function in accordance with Pressure Equipment Directive 2014/68/EU, Article 2, point 4).

Oxygen application (optional)	Verified cleaned, suitable for O ₂ service (wetted parts)
China RoHS symbol	The device is visibly identified according to SJ/T 11363-2006 (China-RoHS).
RoHS	The measuring system complies with the substance restrictions of the Restriction on Hazardous Substances Directive 2011/65/EU (RoHS 2).
PROFINET over Ethernet-APL certification	<p>PROFINET over Ethernet-APL interface</p> <p>The device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e. V.). The measuring system meets all the requirements of the following specifications:</p> <ul style="list-style-type: none"> ■ Certified according to: <ul style="list-style-type: none"> ■ Test specification for PROFINET devices ■ PROFINET Security Level – Netload Class ■ The device can also be operated with certified devices of other manufacturers (interoperability)
Additional certification	<p>Classification of process sealing between electrical systems and (flammable or combustible) process fluids according to UL 122701 (formerly ANSI/ISA 12.27.01)</p> <p>Endress+Hauser devices are designed in compliance with UL 122701 (formerly ANSI/ISA 12.27.01), allowing users to eliminate the need for external secondary process seals in the piping, as specified in the process seal sections of ANSI/NFPA 70 (NEC) and CSA 22.1 (CEC), thereby saving on costs. These devices comply with North American installation practices and provide a highly secure and cost-effective installation solution for pressure-bearing applications involving hazardous media. The devices are assigned to "single seal" as follows:</p> <p>CSA C/US IS, XP, NI:</p> <p>Up to 40 bar (600 psi).</p> <p>Further information can be found in the control drawings of the relevant devices.</p> <p>Metrological approval</p> <p>If you select the "China" order option, the device is delivered with a Chinese nameplate according to the Chinese Quality Act.</p>

Order information

Ordering information

Detailed ordering information is available from the nearest sales organization www.addresses.endress.com or in the Product Configurator under www.endress.com:

1. Select the product using the filters and search field.
2. Open the product page.

The **Configuration** button opens the Product Configurator.



Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: direct input of information specific to the measuring point, such as the measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Scope of delivery

The scope of delivery comprises:

- Device
- Optional accessories

Accompanying documentation:

- Brief Operating Instructions
- Final inspection report
- Additional Safety Instructions for devices with approvals (e.g. ATEX, IECEx, NEPSI, etc.)
- Optional: factory calibration form, test certificates



The Operating Instructions are available on the Internet at:

www.endress.com → Download

Service

The following services, among others, can be selected using the Product Configurator.

- Cleaned of oil+grease (wetted)
- Verified cleaned, suitable for O₂ applic. (wetted)
- PWIS-free (paint-wetting impairment substances)
(The plastic protective cover is excluded from the PWIS cleaning)
- ANSI Safety Red coating, coated housing cover
- Set HART burst mode PV
- Set max. alarm current
- Bluetooth communication is disabled on delivery
- Product documentation on paper
A printed (hard copy) version of test reports, declarations and inspection certificates can optionally be ordered via the **Service**, Version, **Product documentation on paper** option. The required documents can be selected under the feature **Test, certificate, declaration** and are then included with the device on delivery.

Measuring point (TAG)

- Order code: marking
- Option: Z1, tagging (TAG), see additional specification
- Location of tag identifier: to be selected in the additional specifications
 - Stainless steel wired-on tag plate
 - Paper adhesive label
 - Plate provided
 - RFID tag
 - RFID tag + stainless steel wired-on tag plate
 - RFID tag + paper adhesive label
 - RFID tag + supplied label/plate
- Definition of tag name: to be defined in the additional specifications
3 lines of maximum 18 characters each
The specified tag name appears on the selected label and/or the RFID TAG
- Identification on electronic nameplate (ENP): 32 digits

**Test reports, declarations
and inspection certificates**

All test reports, declarations and inspection certificates are provided electronically in the *Device Viewer*:

Enter the serial number from the nameplate

(<https://www.endress.com/de/pages/supporting-tools/device-viewer>)



Product documentation on paper

Test reports, declarations and inspection certificates in hard copy can optionally be ordered with feature 570 "Service", Version I7 "Product documentation on paper". The documents are then provided with the device upon delivery.

Accessories

Device-specific accessories

Mechanical accessories

- Mounting bracket for housing
- Mounting bracket for block & bleed valves
- Block&Bleed valves:
 - Block&Bleed valves can be ordered as **enclosed** accessories (seal for mounting is enclosed)
 - Block and bleed valves can be ordered as **mounted** accessories (mounted manifolds are supplied with a documented leak test)
 - Certificates (e.g. 3.1 material certificate and NACE) and tests (e.g. PMI and pressure test) that are ordered with the device apply for the transmitter and the manifold.
 - During the operating life of the valves, it may be necessary to re-tighten the pack.
- Siphons (PZW)
- Flushing rings
- Weather protective cover



For technical data (e.g. materials, dimensions or order numbers), see the accessory document SD01553P.

Plug connectors

- Plug connector M12 90 deg, IP67 5m cable, union nut, Cu Sn/Ni
- Plug connector M12, IP67 union nut, Cu Sn/Ni
- Plug connector M12, 90 deg IP67 union nut, Cu Sn/Ni



The IP protection classes are only maintained if the dummy cap is used or the cable is connected.

Weld-in accessory



For details, refer to TI00426F/00/EN "Weld-in adapters, process adapters and flanges".


Device Viewer

All the spare parts for the device, along with the order code, are listed in the *Device Viewer* (<https://www.endress.com/de/pages/supporting-tools/device-viewer>).

Documentation

The following document types are available in the Downloads area of the Endress+Hauser website (www.endress.com/downloads), depending on the device version:

Document type	Purpose and content of the document
Technical Information (TI)	Planning aid for your device The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.
Brief Operating Instructions (KA)	Guide that takes you quickly to the 1st measured value The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning.
Operating Instructions (BA)	Your reference document The Operating Instructions contain all the information that is required in various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal.
Description of Device Parameters (GP)	Reference for your parameters The document provides a detailed explanation of each individual parameter. The description is aimed at those who work with the device over the entire life cycle and perform specific configurations.

Document type	Purpose and content of the document
Safety instructions (XA)	<p>Depending on the approval, safety instructions for electrical equipment in hazardous areas are also supplied with the device. These are an integral part of the Operating Instructions.</p> <p> The nameplate indicates which Safety Instructions (XA) apply to the device.</p>
Supplementary device-dependent documentation (SD/FY)	<p>Always comply strictly with the instructions in the relevant supplementary documentation. The supplementary documentation is a constituent part of the device documentation.</p>

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas USA

PROFINET®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

Bluetooth®

The Bluetooth® wordmark and logos are registered trademarks of Bluetooth SIG, Inc. and any use of these trademarks by Endress+Hauser is licensed. Other trademarks and trade names are those of their respective owners.

Apple®

Apple, the Apple logo, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc.

Android®

Android, Google Play and the Google Play logo are trademarks of Google Inc.

KALREZ®

Registered trademark of DuPont Performance Elastomers L.L.C., Wilmington, USA



www.addresses.endress.com
