

Safety Instructions

Deltabar PMD63B, PMD75B, PMD78B

ATEX, IECEx: Ex ia IIC T6...T1 Ga



Deltabar PMD63B, PMD75B, PMD78B

Table of contents

About this document 4

Associated documentation 4

Supplementary documentation 4

Certificates and declarations 5

Manufacturer address 5

Other standards 5

Extended order code 5

Safety instructions: General 8

Safety instructions: Specific conditions of use 8

Safety instructions: Installation 9

Temperature tables 10

Connection data 11

About this document

The document number of these Safety Instructions (XA) must match the information on the nameplate.

Associated documentation

All documentation is available on the Internet:

www.endress.com/Deviceviewer

(enter the serial number from the nameplate).



If not yet available, a translation into EU languages can be ordered.

To commission the device, please observe the Operating Instructions pertaining to the device:

PMD63B

HART

BA02552P, TI01858P

PROFIBUS PA

BA02553P, TI01858P

PROFINET

BA02551P, TI01858P

PMD75B

HART

BA02014P, TI01511P

PROFIBUS PA

BA02528P, TI01511P

PROFINET

BA02231P, TI01511P

PMD78B

HART

BA02015P, TI01512P

PROFIBUS PA

BA02529P, TI01512P

PROFINET

BA02232P, TI01512P

Supplementary documentation

Explosion protection brochure: CP00021Z

The explosion protection brochure is available on the Internet:

www.endress.com/Downloads

Certificates and declarations**EU Declaration of Conformity**

Declaration Number:

EU_01087

The EU Declaration of Conformity is available on the Internet:

www.endress.com/Downloads

EU type-examination certificate

Certificate number:

SEV 20ATEX0387 X

List of applied standards: See EU Declaration of Conformity.

IEC Declaration of Conformity

Certificate number:

IECEX SEV 20.0009 X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- IEC 60079-0 : 2017
- IEC 60079-11 : 2023
- IEC TS 60079-47 : 2021

Manufacturer address

Endress+Hauser SE+Co. KG

Hauptstraße 1

79689 Maulburg, Germany

Address of the manufacturing plant: See nameplate.

Other standards

Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres - Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres - Explosion prevention and protection - Part 1: Basic concepts and methodology"

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

PMD63B, PMD7xB	–	*****	+	A*B*C*D*E*F*G*..
(Device type)		(Basic specifications)		(Optional specifications)

* = Placeholder
At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Deltabar

-  The following specifications reproduce an extract from the product structure and are used to assign:
- This documentation to the device (using the extended order code on the nameplate).
 - The device options cited in the document.

Device type

PMD63B, PMD75B, PMD78B

Basic specifications

Position 1, 2 (Approval)		
Selected option		Description
PMD63B	BA	ATEX II 1 G Ex ia IIC T6...T1 Ga
PMD7xB		IECEX Ex ia IIC T6...T1 Ga

Position 3, 4 (Output)		
Selected option		Description
PMD63B	BA	2-wire, 4-20 mA HART
PMD7xB	DA	2-wire, PROFIBUS PA
	Fx	2-wire, Ethernet-APL, 10 Mbit/s

Position 6 (Housing, Material)		
Selected option		Description
PMD63B	D	Single compartment; 316L, hygiene
	J	Dual compartment; Alu, coated
PMD63B PMD75B	B	Single compartment; Alu, coated
PMD7xB	J	Dual compartment; Alu, coated
	K, L	Dual compartment; 316L
	M	Dual compartment L-shape; Alu, coated

Optional specifications

ID Jx, Kx (Test, Certificate, Declaration)		
Selected option		Description
PMD7xB	JL	Ambient temp. transmitter -50 °C (-58 °F), sensor see specification

ID Nx, Ox (Accessory Mounted)		
Selected option		Description
PMD63B PMD7xB	NA	Overvoltage protection ¹⁾

1) Only in connection with Position 6 = J, K, L, M

ID Px, Rx (Accessory Enclosed)		
Selected option		Description
PMD63B	PA	Weather protection cover, 316L ¹⁾
PMD7xB		
PMD75B	PB	Weather protection cover, plastic ²⁾

1) Only in connection with Position 6 = J, K, L, M

2) Only in connection with Position 6 = B

Safety instructions:
General

- The device is intended to be used in explosive atmospheres as defined in the scope of IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Comply with the installation and safety instructions in the Operating Instructions.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ...)
 - Of isolated capacities (e.g. isolated metallic plates)
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.


Safety instructions:
Specific conditions of use

- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
 - Observe the danger of electrostatic charging and discharge.
 - Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges.
- Avoid sparks caused by impact and friction.

Optional specification, ID Px, Rx = PA

Connect the weather protection cover to the local potential equalization.

Safety instructions: Installation



A0041997

- A Zone 0, Electronic
- B Zone 0, Process
- 1 Associated intrinsically safe power supply units
- 2 PMD63B, PMD75B, PMD78B

- After aligning (rotating) the enclosure, retighten the fixing screw.
- Continuous service temperature of the connecting cable: $\geq T_a + 20\text{ K}$.
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- Observe the maximum process conditions according to the manufacturer's Operating Instructions.
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.

Intrinsic safety

- The device is only suitable for connection to certified, intrinsically safe equipment with explosion protection Ex ia.
- The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least $500\text{ V}_{\text{rms}}$.

Optional specification, ID Nx, Ox = NA

The intrinsically safe input power circuit of the device is isolated from ground. The dielectric strength is at least $290\text{ V}_{\text{rms}}$.

Potential equalization

Integrate the device into the local potential equalization.

Temperature tables

- 
 - The specified ambient and process temperature ranges exclusively refer to the explosion protection and must not be exceeded. Operationally permitted ambient temperature ranges can be restricted depending on the version: See Operating Instructions.
 - Do not exceed the max. ambient temperature at the enclosure.
 - The process temperatures refer to the temperature at the separation membrane.
- 

Optional specification, ID Jx, Kx = JL
Lower limit of the ambient temperature for explosion protection changes to -50 °C.

Optional specification, ID Px, Rx = PB
When using the weather protection cover: Reduce the admissible ambient temperature by 10 K.

Device Type PMD63B

Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)	
		Basic specification, Position 6 = B, J	
T6	+80 °C	-40 to +55 °C	-40 to +50 °C
T4	+130 °C	-40 to +65 °C	-40 to +65 °C
T3	+190 °C	-40 to +65 °C	-40 to +65 °C
T2	+290 °C	-40 to +65 °C	-40 to +65 °C
T1	+400 °C	-40 to +65 °C	-40 to +65 °C

Device Type PMD75B

Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
T6	+60 °C	-40 to +60 °C
	+70 °C	-40 to +55 °C
	+80 °C	-40 to +55 °C
T4...T1	+60 °C	-40 to +65 °C
	+85 °C	-40 to +60 °C
	+100 °C	-40 to +55 °C

Device Type PMD78B

Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
T6	+80 °C	−40 to +55 °C
T4	+130 °C	−40 to +65 °C
T3	+190 °C	−40 to +65 °C
T2	+290 °C	−40 to +65 °C
T1	+400 °C	−40 to +65 °C

Version with separate enclosure

Temperature class	Process temperature T _p (process)	Ambient temperature T _a (ambient)
T6	+80 °C	−20 to +60 °C
T4...T1	+100 °C	−20 to +60 °C

Connection data

Basic specification, Position 3, 4 = BA

Power supply
U _I ≤ 30 V _{DC} I _I ≤ 300 mA P _I ≤ 1 W C _I ≤ 10 nF L _I = 0

Basic specification, Position 3, 4 = DA

Power supply	
FISCO	Entity
$U_i \leq 17.5 \text{ V}_{DC}$	$U_i \leq 24 \text{ V}_{DC}$
$I_i \leq 380 \text{ mA}$	$I_i \leq 300 \text{ mA}$
$P_i \leq 5.32 \text{ W}$	$P_i \leq 1.2 \text{ W}$
$C_i \leq 5 \text{ nF}$	$C_i \leq 5 \text{ nF}$
$L_i = 0$	$L_i = 0$

Basic specification, Position 3, 4 = Fx

Power supply	
2-WISE	Entity
$U_i \leq 17.5\text{ V}_{DC}$	$U_i \leq 17.5\text{ V}_{DC}$
$I_i \leq 380\text{ mA}$	$I_i \leq 300\text{ mA}$
$P_i \leq 5.32\text{ W}$	$P_i \leq 1.2\text{ W}$
$C_i \leq 5\text{ nF}$	$C_i \leq 5\text{ nF}$
$L_i = 0$	$L_i = 0$



71725941

www.addresses.endress.com
