

Technical Information

iTHERM TS111

Insert for installation in thermometers



Applications

- For universal use
- RTD measuring range: -200 to 600 °C (-328 to 1 112 °F)
- TC measuring range: -40 to 1 100 °C (-40 to 2 012 °F)
- For installation in thermometers

Head transmitter

All Endress+Hauser transmitters are available with enhanced measurement accuracy and reliability compared to directly wired sensors. They offer easy customizing, with a choice of the following outputs and communication protocols:

- Analog output 4 to 20 mA
- HART®
- PROFIBUS® PA
- FOUNDATION Fieldbus™
- PROFINET® with Ethernet-APL
- IO-Link®

Your benefits

- Quick replacement during operation with modular thermometers
- Highly flexible thanks to customized immersion lengths
- High degree of compatibility and design as per IEC 60751
- Extremely vibration-resistant
- Very fast response times
- Types of protection for use in hazardous locations:
 - Intrinsically safe (Ex ia)
 - Non-sparking (Ex nA)
 - For use in flameproof enclosures (Ex d)

Table of contents

Function and system design	3
Measuring principle	3
Input	3
Measuring range	3
Output	3
Output signal	3
Family of temperature transmitters	4
Electrical connection	4
Terminal assignment	4
Performance characteristics	8
Maximum measurement error	8
Self-heating	9
Response time	9
Calibration	10
Insulation resistance	12
Dielectric strength	12
Transmitter specifications	12
Installation	12
Orientation	12
Installation instructions	12
Immersion length	13
Environment	14
Ambient temperature range	14
Vibration resistance	14
Impact resistance	15
Mechanical construction	15
Design and dimensions	15
Materials	19
Certificates and approvals	19
MID	19
Ordering information	19
Accessories	20
Online tools	20
Documentation	20

Function and system design

Measuring principle

Resistance thermometers (RTD)

The insert is a universal, replaceable temperature measuring element in accordance with DIN 43735 for modular thermometers and thermowells in accordance with DIN 43772. It enables the use of a Pt100 resistance thermometer in accordance with IEC 60751. The Pt100 is a platinum resistor with 100 Ω at 0 °C (32 °F) and a temperature coefficient of $\alpha = 0.003851^\circ \text{C}^{-1}$.

Platinum resistance thermometers are available in two designs:

- **Wire-wound (WW):** Double winding of platinum wire in a ceramic carrier, sealed with a ceramic protective layer. High repeatability and long-term stability up to 600 °C (1 112 °F), but large design and sensitive to vibration.
- **Thin-film sensors (TF):** Thin platinum layer ($\approx 1 \mu\text{m}$) on ceramic substrate, structured using photolithography. The platinum conductor paths formed in this way create the measuring resistance. Cover and passivation layers protect from contamination and oxidation, even at high temperatures.

Thin-film temperature sensors (TF) are smaller and more vibration-resistant than wire-wound designs. At high temperatures, their characteristic curve deviates slightly from IEC 60751, meaning that tolerance class A is only maintained up to approx. 300 °C (572 °F).

Thermocouples (TC)

Thermocouples are robust sensors for temperature measurement based on the Seebeck Effect. They measure temperature differences between the measuring point and reference junction; the absolute temperature is determined by compensation. The material combinations used and their thermoelectric voltage characteristics are standardized in IEC 60584 or ASTM E230/ANSI MC96.1.

Input

Measuring range

RTD resistance thermometer

Sensor type	Measuring range	Type of connection	Temperature-sensitive length
Pt100 (IEC 60751, TF) iTHERM StrongSens	-50 to 500 °C (-58 to 932 °F)	3- or 4-wire	7 mm (0.27 in)
iTHERM QuickSens	-50 to 200 °C (-58 to 392 °F)	3- or 4-wire	5 mm (0.20 in)
Pt100 thin-film sensor (TF)	-50 to 400 °C (-58 to 752 °F)	3- or 4-wire	10 mm (0.39 in)
Pt100 wire-wound sensor (WW)	-200 to 600 °C (-328 to 1 112 °F)	3- or 4-wire	10 mm (0.39 in)

TC thermocouples:

Sensor type	Measuring range	Type of connection	Temperature-sensitive length
Thermocouple type K	-40 to 1 100 °C (-40 to 2 012 °F)	Grounded or insulated connection	Insert length
Thermocouple type J	-40 to 750 °C (-40 to 1 382 °F)	Grounded or insulated connection	Insert length
Thermocouple type N	-40 to 1 100 °C (-40 to 2 012 °F)	Grounded or insulated connection	Insert length

Output

Output signal

Generally, the measured value can be transmitted in one of two ways:

- Directly-wired sensors - sensor measured values forwarded without a transmitter.
- Via all common protocols by selecting an appropriate Endress+Hauser iTEMP temperature transmitter. All the transmitters listed below are mounted directly in the washer of the insert and wired with the sensory mechanism. This part of the insert is later inserted into the terminal head of the thermometer.

Family of temperature transmitters

Thermometers fitted with iTEMP transmitters are an installation-ready complete solution to improve temperature measurement by significantly increasing measurement accuracy and reliability, when compared to direct wired sensors, as well as reducing both wiring and maintenance costs.

4-20 mA head transmitter

They offer a high degree of flexibility, thereby supporting universal application with low inventory storage. The iTEMP transmitters can be configured quickly and easily at a PC. Endress+Hauser offers free configuration software which can be downloaded from the Endress+Hauser website.

HART head transmitter

The iTEMP transmitter is a 2-wire device with one or two measuring inputs and one analog output. The device not only transfers converted signals from resistance thermometers and thermocouples, it also transfers resistance and voltage signals using HART communication. Swift and easy operation, visualization and maintenance using universal configuration software like FieldCare, DeviceCare or FieldCommunicator 375/475. Integrated Bluetooth® interface for the wireless display of measured values and configuration via Endress +Hauser SmartBlue app, optional.

PROFIBUS PA head transmitter

Universally programmable iTEMP head transmitter with PROFIBUS PA communication. Conversion of various input signals into digital output signals. High measurement accuracy over the complete operating temperature range. PROFIBUS PA functions and device-specific parameters are configured via fieldbus communication.

FOUNDATION Fieldbus™ head transmitters

Universally programmable iTEMP head transmitter with FOUNDATION Fieldbus™ communication. Conversion of various input signals into digital output signals. High measurement accuracy over the complete operating temperature range. All iTEMP transmitters are approved for use in all the main process control systems. The integration tests are performed in Endress+Hauser's 'System World'.

Head transmitter with PROFINET and Ethernet-APL™

The iTEMP transmitter is a 2-wire device with two measuring inputs. The device not only transfers converted signals from resistance thermometers and thermocouples, it also transfers resistance and voltage signals using the PROFINET protocol. Power is supplied via the 2-wire Ethernet connection according to IEEE 802.3cg 10Base-T1. The iTEMP transmitter can be installed as an intrinsically safe electrical apparatus in Zone 1 hazardous areas. The device can be used for instrumentation purposes in the terminal head form B (flat face) according to DIN EN 50446.

Head transmitter with IO-Link

The iTEMP transmitter is an IO-Link device with a measurement input and an IO-Link interface. It offers a configurable, simple and cost-effective solution thanks to digital communication via IO-Link. The device is mounted in a terminal head form B (flat face) as per DIN EN 5044.

Advantages of the iTEMP transmitters:

- Dual or single sensor input (optionally for certain transmitters)
- Attachable display (optionally for certain transmitters)
- Unsurpassed reliability, accuracy and long-term stability in critical processes
- Mathematical functions
- Monitoring of the thermometer drift, sensor backup functionality, sensor diagnostic functions
- Sensor-transmitter-matching based on the Callendar van Dusen coefficients (CvD).


Electrical connection

Terminal assignment



The sensor connection wires are equipped with terminal lugs. The nominal diameter of the cable lug is 1.3 mm (0.05 in)


RTD sensor connection type



A0045453

1 Mounted ceramic terminal block


- 1 3-wire
- 2 2x3-wire
- 3 4-wire
- 4 Outside screw



A0045464

2 Head-mounted iTEMP TMT7x transmitter or iTEMP TMT31 (single sensor input)


- 1 Sensor input, RTD, 4-, 3- and 2-wire
- 2 Power supply/bus connection
- 3 Display connection/CDI interface



A0052495

3 Head-mounted iTEMP TMT36 transmitter (single sensor input)

- 1 RTD sensor input: 4-, 3- and 2-wire
- 2 Display connection
- L+ 18 to 30 V_{DC} power supply
- L- 0 V_{DC} power supply
- C/Q IO-Link or switch output




A0045466

4 Head-mounted iTEMP TMT8x transmitter (dual sensor input)


- 1 Sensor input 1, RTD, 4- and 3-wire
- 2 Sensor input 2, RTD, 3-wire
- 3 Fieldbus connection and power supply
- 4 Display connection

Thermocouple (TC) sensor connection type



A0012700


5 Installed ceramic terminal block for thermocouples.



A0045353

6 Head-mounted iTEMP TMT7x transmitter or iTEMP TMT31 (single sensor input)

- 1 Sensor input
- 2 Power supply and bus connection
- 3 Display connection and CDI interface



7 Head-mounted iTEMP TMT8x transmitter (dual sensor input)


- 1 Sensor input 1
- 2 Sensor input 2
- 3 Fieldbus connection and power supply
- 4 Display connection

Thermocouple wire colors

As per IEC 60584	As per ASTM E230
<ul style="list-style-type: none">■ Type J: black (+), white (-)■ Type K: green (+), white (-)■ Type N: pink (+), white (-)	<ul style="list-style-type: none">■ Type J: white (+), red (-)■ Type K: yellow (+), red (-)■ Type N: orange (+), red (-)

Performance characteristics

Maximum measurement error RTD resistance thermometers as per IEC 60751:



1) $|t|$ = Temperature absolute value in °C

i To obtain the maximum tolerances in °F, multiply the results in °C by a factor of 1.8.

Temperature ranges

Sensor type ¹⁾	Operating temperature range	Class B	Class A	Class AA
Pt100 (WW)	-200 to 600 °C (-328 to 1112 °F)	-200 to 600 °C (-328 to 1112 °F)	-100 to 450 °C (-148 to 842 °F)	-50 to 250 °C (-58 to 482 °F)
Pt100 (TF) Basic	-50 to 200 °C (-58 to 392 °F)	-50 to 200 °C (-58 to 392 °F)	-30 to 200 °C (-22 to 392 °F)	-
Pt100 (TF) Standard	-50 to 400 °C (-58 to 752 °F)	-50 to 400 °C (-58 to 752 °F)	-30 to 250 °C (-22 to 482 °F)	0 to 150 °C (32 to 302 °F)
Pt100 (TF) iTHERM QuickSens	-50 to 200 °C (-58 to 392 °F)	-50 to 200 °C (-58 to 392 °F)	-30 to 200 °C (-22 to 392 °F)	0 to 150 °C (32 to 302 °F)
Pt100 (TF) iTHERM StrongSens	-50 to 500 °C (-58 to 932 °F)	-50 to 500 °C (-58 to 932 °F)	-30 to 300 °C (-22 to 572 °F)	0 to 150 °C (32 to 302 °F)

1) Options depend on product and configuration

TC thermocouples: Permitted deviation limits of thermoelectric voltages from standard characteristic for thermocouples as per IEC 60584 and ASTM E230/ANSI MC96.1:

Standard	Type	Standard tolerance		Special tolerance	
		Class	Deviation	Class	Deviation
IEC 60584					
	J (Fe-CuNi)	2	$\pm 2.5\text{ °C}$ (–40 to 333 °C) $\pm 0.0075\text{ t }^{1)}$ (333 to 750 °C)	1	$\pm 1.5\text{ °C}$ (–40 to 375 °C) $\pm 0.004\text{ t }^{1)}$ (375 to 750 °C)
	K (NiCr-NiAl) N (NiCrSi-NiSi)	2	$\pm 2.5\text{ °C}$ (–40 to 333 °C) $\pm 0.0075\text{ t }^{1)}$ (333 to 1200 °C)	1	$\pm 1.5\text{ °C}$ (–40 to 375 °C) $\pm 0.004\text{ t }^{1)}$ (375 to 1000 °C)

1) |t| = absolute value °C

Self-heating

RTD elements are passive resistance temperature sensors, which must be supplied with a measuring current in order to determine the measured values. This measurement current causes a self-heating effect in the RTD element itself which in turn creates an additional measurement error. The extent of this measurement error is influenced not only by the measuring current but also by the temperature conductivity and the thermal coupling of the resistance sensor with the environment. The self-heating is negligible if an iTEMP temperature transmitter (extremely low measuring current) from Endress+Hauser is used.

Sensor type	Ø ID	Typical values for self-heating (measured in water at 20 °C)
Pt100 (TF) standard	Ø3 mm (0.12 in)	36mΩ/mW or 94 mK/mW
	Ø6 mm (0.24 in)	120mΩ/mW or 310 mK/mW
Pt100 (TF) iTHERM StrongSens	Ø6 mm (0.24 in)	≤ 25 mΩ/mW or ≤ 64 mK/mW
Pt100 (TF) iTHERM QuickSens	Ø3 mm (0.12 in)	13mΩ/mW or 35 mK/mW
	Ø6 mm (0.24 in)	11.5mΩ/mW or 30 mK/mW
Pt100 (WW)	Ø3 mm (0.24 in)	15mΩ/mW or 39 mK/mW
	Ø6 mm (0.24 in)	50mΩ/mW or 130 mK/mW
Pt100 (TF) basic	Ø6 mm (0.24 in)	120mΩ/mW or 310 mK/mW

Response time

RTD resistance thermometers tested in accordance with IEC 60751 in flowing water (0.4 m/s at 30 °C):

Insert			
Sensor type	Ø ID	Response time	
Pt100 (TF) standard	Ø3 mm (0.12 in)	t ₅₀ t ₉₀	< 2.5 s < 5.5 s
	Ø6 mm (0.24 in)	t ₅₀ t ₉₀	< 5.0 s < 13 s
Pt100 (TF) iTHERM StrongSens	Ø6 mm (0.24 in)	t ₅₀ t ₉₀	< 5.5 s < 16 s
Pt100 (TF) iTHERM QuickSens	Ø3 mm (0.12 in)	t ₅₀ t ₉₀	< 0.5 s < 1.2 s
	Ø6 mm (0.24 in)	t ₅₀ t ₉₀	< 0.5 s < 1.5 s
Pt100 (WW)	Ø3 mm (0.12 in)	t ₅₀ t ₉₀	< 2 s < 5 s
	Ø6 mm (0.24 in) single sensor	t ₅₀ t ₉₀	< 4 s < 10.5 s
	Ø6 mm (0.24 in) double sensor	t ₅₀ t ₉₀	< 4.5 s < 12 s

Insert			
Sensor type	Ø ID	Response time	
Pt100 (TF) basic	Ø6 mm (0.24 in) single sensor	t ₅₀ t ₉₀	<6.5 s <15.5 s
	Ø6 mm (0.24 in) double sensor	t ₅₀ t ₉₀	<9.5 s <22.5 s

TC thermocouples:

Insert			
Sensor type	Diameter ID	Response time	
Thermocouples (K, J and N)	Ø3 mm (0.12 in)	t ₅₀ t ₉₀	1 s 3 s
	Ø6 mm (0.24 in)	t ₅₀ t ₉₀	2.5 s 6 s



The response time applies to the insert without transmitter.

Calibration

Calibration of thermometers

Calibration involves comparing the measured values of a unit under test (UUT) with those of a more precise calibration standard using a defined and reproducible measurement method. The aim is to determine the deviation or measurement errors of the UUT's measured values from the true value of the measured variable. Two different methods are used for thermometers:

- Calibration at fixed points, e.g. at the freezing point, the solidification point, of water at 0 °C,
- Calibration by comparison with a precise reference thermometer

The thermometer to be calibrated must display the fixed point temperature or the temperature of the reference thermometer as accurately as possible. For thermometer calibrations, temperature-controlled calibration baths with highly homogeneous thermal values or special calibration furnaces are typically used. The measurement uncertainty may increase due to heat conduction errors and short immersion lengths. The existing measurement uncertainty is recorded on the individual calibration certificate. For accredited calibrations according to ISO17025, the measurement uncertainty must not exceed twice the accredited measurement uncertainty. If this limit is exceeded, only a factory calibration can be carried out.

The measured value of the UUT is determined using the maximum possible immersion depth and the specific measuring conditions and measurement results are documented on an evaluation certificate.

Sensor-transmitter-matching

The resistance/temperature curve of platinum resistance thermometers is standardized but in practice cannot be maintained exactly over the entire operating temperature range. Platinum resistance sensors are therefore divided into tolerance classes, such as Class A, AA or B as per IEC 60751. These tolerance classes describe the maximum permissible deviation of the specific sensor characteristic curve from the standard characteristic curve, i.e. the maximum permissible temperature-dependent characteristic error. Converting the measured sensor resistance values to temperatures in temperature transmitters or other measuring electronics is often associated with a considerable error, as this conversion is generally based on the standard characteristic curve.

When Endress +Hauser temperature transmitters are used, this conversion error can be reduced significantly by sensor-transmitter matching:

- Calibration at three temperatures at least and determination of the actual temperature sensor characteristic curve,
- adjustment of the sensor-specific polynomial function using Calendar-van Dusen (CvD) coefficients,
- Configuration of the temperature transmitter with the sensor-specific CvD coefficients for resistance/temperature conversion, and
- another calibration of the reconfigured temperature transmitter with connected resistance thermometer.

Endress+Hauser offers its customers this kind of sensor-transmitter matching as a separate service. Furthermore, the sensor-specific polynomial coefficients of platinum resistance thermometers are, where possible, stated on every Endress+Hauser calibration certificate. For example, at least three

calibration points are specified so that suitable temperature transmitters can also be configured accordingly by the user.


For the device, Endress+Hauser offers standard calibrations at a reference temperature of -80 to $600\text{ }^{\circ}\text{C}$ (-112 to $1\,112\text{ }^{\circ}\text{F}$) based on the ITS90 (International Temperature Scale). Calibrations in other temperature ranges are available from your Endress+Hauser sales center on request. Calibrations are traceable to national and international standards. The calibration certificate is referenced to the serial number of the device. Only the insert is calibrated.

Minimum insertion length (IL) for inserts required to perform a correct calibration

i Due to the limitations of furnace geometries, the minimum insertion lengths must be observed at high temperatures to enable a calibration to be performed with an acceptable degree of measurement uncertainty. The same applies when using a head transmitter. Due to heat conduction, minimum lengths must be observed in order to guarantee the functionality of the transmitter -40 to $85\text{ }^{\circ}\text{C}$ (-40 to $185\text{ }^{\circ}\text{F}$)

Calibration temperature	Minimum insertion length IL in mm without head transmitter
$-196\text{ }^{\circ}\text{C}$ ($-320.8\text{ }^{\circ}\text{F}$)	120 mm (4.72 in) ¹⁾
-80 to $250\text{ }^{\circ}\text{C}$ (-112 to $482\text{ }^{\circ}\text{F}$)	No minimum insertion length required ²⁾
251 to $550\text{ }^{\circ}\text{C}$ (483.8 to $1\,022\text{ }^{\circ}\text{F}$)	300 mm (11.81 in)
551 to $600\text{ }^{\circ}\text{C}$ ($1\,023.8$ to $1\,112\text{ }^{\circ}\text{F}$)	400 mm (15.75 in)

- 1) Min. 150 mm (5.91 in) Required for iTEMP head transmitters
- 2) At a temperature of 80 to 250 °C (176 to 482 °F) and with iTEMP head transmitters, a minimum of 50 mm (1.97 in) is required



8 Insertion lengths for sensor calibration

IL Insertion length for factory calibration or recalibration onsite without the iTHERM QuickNeck extension neck
ILa Insertion length for recalibration onsite with the iTHERM QuickNeck extension neck
ΔL Additional length, depending on the calibration rig, if the insert cannot be fully immersed

- To check the actual measurement accuracy rating of the thermometers installed, a cyclic calibration of the installed sensor needs to be performed frequently. The insert is normally removed for comparison with a precise reference thermometer in the calibration bath (see graphic, left part).
- The iTHERM QuickNeck enables quick, tool-free removal of the insert for calibration purposes. The entire upper part of the thermometer is released by turning the terminal head. The insert is removed from the thermowell and directly immersed into the calibration bath (see graphic, right part). Make sure that the cable is long enough to be able to reach the mobile calibration bath with the cable connected. If this is not possible for the calibration, it is advisable to use a connector.

Advantages of iTHERM QuickNeck:

- Considerable time savings when recalibrating the device (up to 20 minutes per measuring point)
- Wiring mistakes avoided when re-installing
- Minimum plant downtime, thereby saving costs

Insulation resistance

RTD resistance thermometers

Insulation resistance as per IEC 60751 with a minimum test voltage of 100 V DC:
>100 MΩ at 25 °C

TC thermocouples

Insulation resistance as per DIN EN 60584 between the connecting wires and the sheath material with a minimum test voltage of 500 V DC:

- >1 GΩ at 25 °C
- >5 MΩ at 500 °C

Dielectric strength

Dielectric strength between terminals and insert sheath (for RTD only):

- For all Ø6 mm (0.24 in) inserts: ≥ 1 000 V DC over 5 s
- For Ø 3 mm (0.12 in) iTHERM QuickSens: ≥500 V DC over 5 s
- For all other Ø3 mm (0.12 in) inserts: ≥ 250 V DC over 5 s

Transmitter specifications

	Pt100 measurement accuracy	Sensor current	Galvanic isolation
iTEMP TMT82 HART RTD, TC, Ω, mV	0.08 °C (0.14 °F) 0.1 °C (0.18 °F) ¹⁾	I ≤ 0.3 mA	U = 2 kV AC
iTEMP TMT84 PA iTEMP TMT85 FF RTD, TC, Ω, mV	0.08 °C (0.14 °F) digital		
iTEMP TMT71	0.07 °C (0.13 °F) digital 0.1 °C (0.18 °F) ¹⁾	I ≤ 0.3 mA	U = 2 kV AC
iTEMP TMT72 HART RTD, TC, Ω, mV	0.1 °C (0.18 °F) ¹⁾		

1) At current output

Installation


Orientation

No restrictions.

Installation instructions

Install the iTHERM TS111 insert in thermometers with a flat face terminal head as per DIN EN 50446. When installing in a thermometer with a thermowell, the insert is secured in the thermometer's terminal head by means of spring loaded screws. This means that the insert tip is always pressed against the internal floor of the thermowell, thereby ensuring good thermal contact.

The prerequisite is an insert length (IL) that is adapted to the thermowell. This can be calculated using the formula $IL = E + T + U + X$ (E = extension neck length, T = thermowell extension, U = immersion length of thermowell, X = variable for calculating length of insert). The electrical connection is established as detailed in the "Power supply" section.



A0019385

9 General installation options: in an assembly with thermowell (left), direct measurement (right)

Immersion length

RTD resistance thermometers:

Error caused by heat conduction $\leq 0.1\text{ K}$; measured according to IEC 60751 at 100 °C in liquid medium

Sensor type ¹⁾	ØID	Immersion length
Pt100 (TF) standard	Ø3 mm (0.12 in)	≥ 30 mm (1.18 in)
	Ø6 mm (0.24 in)	≥ 50 mm (1.97 in)
Pt100 (TF) iTHERM StrongSens	Ø6 mm (0.24 in)	≥ 40 mm (1.57 in)
Pt100 (TF) iTHERM QuickSens	Ø3 mm (0.12 in)	≥ 25 mm (0.98 in)
	Ø6 mm (0.24 in)	
Pt100 (WW)	Ø3 mm (0.12 in)	≥ 60 mm (2.36 in)
	Ø6 mm (0.24 in)	
	Ø6.35 mm (¼ in)	
Pt100 (TF) basic	Ø6 mm (0.24 in)	≥ 50 mm (1.97 in)
	Ø6.35 mm (¼ in)	

1) Options depend on product and configuration

TC thermocouples:

Sensor type ¹⁾	ØID	Immersion length
Thermocouple types J, K and N	Ø3 mm (0.12 in)	30 mm (1.18 in)
	Ø6 mm (0.24 in)	
	Ø6.35 mm (¼ in)	


1) Options depend on product and configuration

Possible bending radius

Sensor type ¹⁾	ØID	Bending radius R	Non-bendable length (tip) NL ²⁾
Pt100 (TF) standard	Ø3 mm (0.12 in)	$R \geq 3 \times ID$	30 mm (1.18 in)
	Ø6 mm (0.24 in)		
Pt100 (TF) iTHERM StrongSens	Ø6 mm (0.24 in)	$R \geq 3 \times ID$	30 mm (1.18 in)
Pt100 (TF) iTHERM QuickSens	Ø3 mm (0.12 in)	Non-bendable	Non-bendable
	Ø6 mm (0.24 in)	$R \geq 3 \times ID$	30 mm (1.18 in)
Pt100 (WW)	Ø3 mm (0.12 in)	$R \geq 3 \times ID$	30 mm (1.18 in)
	Ø6 mm (0.24 in)		
	Ø6.35 mm (¼ in)		
Pt100 (TF) basic	Ø6 mm (0.24 in)	Non-bendable	Non-bendable
	Ø6.35 mm (¼ in)		
Thermocouple types J, K, N	Ø3 mm (0.12 in)	$R \geq 3 \times ID$	30 mm (1.18 in)
	Ø6 mm (0.24 in)		
	Ø6.35 mm (¼ in)		

- 1) Options depend on product and configuration
 2) If a sleeve is overlapped, NL increases to 80 mm.

i Inserts with an insertion length $IL > 1\,000$ mm (39.4 in) are coiled when delivered. Users will receive instructions with the insert detailing how to replace the rolled insert.



A0019386

Environment

Ambient temperature range

Terminal head	Temperature in °C (°F)
Without head transmitter installed	Depends on the terminal head used and the cable gland or fieldbus connector
With head transmitter installed	-40 to 85 °C (-40 to 185 °F)
With head transmitter installed and display	-20 to 70 °C (-4 to 158 °F)

Vibration resistance

RTD resistance thermometers:

The Endress+Hauser inserts exceed the requirements of IEC 60751, which specify shock and vibration resistance of 3 g in the range from 10 to 500 Hz.

The vibration resistance at the measuring point depends on the sensor type and design; see the following table:


Sensor type	Vibration resistance for the sensor tip ¹⁾
Pt100 (TF) standard	≤ 4g
Pt100 (TF) iTHERM StrongSens (vibration-resistant)	≤ 600 m/s ² (≤ 60g)
Pt100 (TF) iTHERM QuickSens	3 mm (0.12 in) ≤ 3g 6 mm (0.24 in) ≤ 60g
Pt100 (WW)	≤ 3g
Pt100 (TF) basic	≤ 3g
Thermocouples, type K, J, N (based on IEC 60751)	≤ 3g

1) (measured according to IEC 60751 with varying frequencies in the range of 10 to 500 Hz)

Impact resistance ≥ 4 J (measured according to IEC 60079-0)

Mechanical construction

Design and dimensions



A0019449


10 All dimensions in mm (in).

- 1 Insert with installed iTEMP head transmitter
- 2 Insert with installed head transmitter and sleeve $\varnothing 8$ mm (0.31 in), $\varnothing ID = 6$ mm (0.24 in)
- 3 Insert with flying leads (standard version)
- 4 Thermometer with insert
- E Neck extension length
- $\varnothing ID$ Insert diameter $\varnothing 3$ mm (0.12 in) or $\varnothing 6$ mm (0.24 in)
- IL Measuring insert length
- L Immersion length
- X Variable for calculating the length of the insert
- $\varnothing X$ Thermowell diameter

The insert comprises three main components: a sensor at the tip, an electrical connection at the upper end and in between the two a mineral insulated sheathed cable or a stainless steel tube with insulated wires. In RTD sensors, the sensor element is embedded in a ceramic potting compound in a sensor tip, soldered to the base of the sensor tip, or embedded in compacted mineral insulation, depending on the sensor type.

There are two different designs available for thermocouples:

Grounded version: In this design, the thermocouple is mechanically and electrically connected to the inside of the sheathed cable at the junction. This results in good heat transfer from the sensor sheath to the measuring junction of the thermocouple.



A0026086

Non-grounded version: If the probe is not grounded, there is no connection between the thermocouple and the sensor wall. This is also referred to as an insulated measuring point. The response time is slower than in a grounded version.



A0026087

RTD resistance thermometers:

Sensor type	ØID	Sheathed cable, material
Pt100 (TF) iTHERM StrongSens	Ø6 mm (0.24 in)	The sheath is made of stainless steel and is filled with a magnesium oxide (MgO) powder. The primary sensor is permanently encapsulated in the sensor cap to ensure maximum vibration resistance.
Pt100 (TF) iTHERM QuickSens	Ø 3 mm (0.12 in) ¹⁾	The sheath is made of stainless steel. The primary sensor is welded onto the base of the sensor cap to ensure the shortest response times.
	Ø6 mm (0.24 in)	The sheath is made of stainless steel and is filled with a magnesium oxide (MgO) powder. The primary sensor is welded onto the base of the sensor cap to ensure the shortest response times.
Pt100 (TF) standard	Ø3 mm (0.12 in)/ Ø6 mm (0.24 in)	The sheath is made of stainless steel and is filled with a magnesium oxide (MgO) powder. The primary sensor is embedded in compacted MgO powder in the insert tip.
Pt100 (WW), extended measuring range	Ø3 mm (0.12 in)/ Ø6 mm (0.24 in)	The sheath is made of stainless steel and is filled with a magnesium oxide (MgO) powder. The primary sensor is embedded in compacted MgO powder in the insert tip. The wire-wound sensor enables a measuring range of -200 to 600 °C (-328 to 1 112 °F). Single or double sensor elements are available.
Pt100 (TF) basic	Ø6 mm (0.24 in)	The sheath is made of stainless steel SS316L. The primary sensor, a thin-film Pt100, is installed in the tip of the insert.

- 1) If the insertion length IL > 1 400 mm (55 in), the diameter of the insert is 3 mm (0.12 in) at the sensor tip and 6 mm (0.24 in) at the upper end

iTHERM QuickSleeve

Reducing the air gap between the thermowell and the measuring insert has the greatest impact on improving the response time of the thermometer. Optimizing the bore in the barstock thermowell is the best solution, e.g. a bore diameter of 6.1 mm (0.24 in) when using a 6 mm (0.24 in) measuring insert.





If it is not possible to adapt the bore accordingly, e.g. when using existing thermowells or specifications for using standard bores, the iTHERM QuickSleeve from Endress+Hauser can be used.


iTHERM QuickSleeve is a mechanical spring component at the tip of a measuring insert. This spring component improves heat transfer and shortens the response time from a barstock thermowell to the measuring insert and ultimately to the sensor.

iTHERM QuickSleeve is available in two designs for use in barstock thermowells:

- For bore diameter 6.5 mm (0.256 in)
- For bore diameter 7 mm (0.28 in)

Mechanical construction

Type of fitting	Bore diameter 6.5 mm (0.256 in)	Bore diameter 7 mm (0.28 in)
Pt100 iTHERM QuickSens, 3 mm (0.12 in)	 A0057223	 A0057224
Pt100, WW and TF, 3 mm (0.12 in)	 A0057225	 A0057226

 A0060389	Materials <ul style="list-style-type: none"> ■ Bushing (1) and reinforcing tube (3): Stainless steel ■ Spring (2): Copper-plated
--	---

The spring pre-load of the insert equals 6 mm (0.24 in).

TC thermocouples:

Sensor type	ØID	Sheathed cable, material
Thermocouple type K	Ø3 mm (0.12 in) / Ø6 mm (0.24 in)	The type K thermocouples are available as single or double sensors. The wires made of nickel-chromium and nickel are embedded in magnesium oxide (MgO) powder within the sheathed cable made of Alloy 600. The measuring point can be insulated or grounded (electrically conductive, connected to sheathed cable).
Thermocouple type J	Ø3 mm (0.12 in) / Ø6 mm (0.24 in)	The type J thermocouples are available as single or double sensors. The wires made of iron and copper-nickel are embedded in magnesium oxide (MgO) powder within the sheathed cable made of stainless steel SS316L. The measuring point can be insulated or grounded (electrically conductive, connected to sheathed cable).
Thermocouple type N	Ø3 mm (0.12 in) / Ø6 mm (0.24 in)	The type N thermocouples are available as single or double sensors. The wires made of nickel-chromium-silicon and nickel-silicon are embedded in magnesium oxide (MgO) powder within the sheathed cable made of Alloy TD (Pyrosil, Microbell or similar). The measuring point can be insulated or grounded (electrically conductive, connected to sheathed cable). Compared to type K thermocouples, type N thermocouples are significantly less prone to what is known as "green rot".

The insert comes with free wires that can be used for direct electrical connection to a head transmitter. Alternatively, a ceramic terminal block can be used, which is mounted securely on a washer.

Materials

The temperatures for continuous operation specified in the following table are intended only as reference values during use of the various materials in air. In exceptional cases, the maximum operating temperatures are sometimes significantly lower.

Description	Recommended max. temperature for continuous use in air	Properties
AISI 316L	650 °C (1 202 °F)	<ul style="list-style-type: none"> ▪ Austenitic, stainless steel ▪ High corrosion resistance in general ▪ Particularly high corrosion resistance in chlorine-based and acidic, non-oxidizing atmospheres through the addition of molybdenum (e.g. phosphoric and sulfuric acids, acetic and tartaric acids with a low concentration) ▪ Increased resistance to intergranular corrosion and pitting
Alloy 600	1 100 °C (2 012 °F)	<ul style="list-style-type: none"> ▪ A nickel/chromium alloy with very good resistance to aggressive, oxidizing and reducing atmospheres, even at high temperatures ▪ Resistance to corrosion caused by chlorine gases and chlorinated media as well as many oxidizing mineral and organic acids, sea water etc. ▪ Corrosion from ultrapure water ▪ Not to be used in sulfur-containing atmospheres
Pyrosil (Alloy TD)	1 100 °C (2 012 °F)	<ul style="list-style-type: none"> ▪ Nickel-chromium alloy, which was designed for thermocouple sheaths ▪ High degree of temperature corrosion resistance and robustness without the use of elements that can cause thermocouple contamination over time ▪ Excellent resistance to nitration up to 1 177 °C (2 151 °F) ▪ Resistant to oxide spalling

Certificates and approvals

Current certificates and approvals for the product are available at www.endress.com on the relevant product page:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Downloads**.

MID

Test certificate (only in SIL mode). In compliance with:

- WELMEC 8.8: "Guide on the general and administrative aspects of the voluntary system of modular evaluation of measuring instruments"
- OIML R117-1, Edition 2007 (E), "Dynamic measuring system for liquids other than water"
- EN 12405-1/A2, Edition 2010, "Gas meters - Converters - Part 1: Volume conversion"
- OIML R140-1, Edition 2007 (E), "Measuring systems for gaseous fuels"

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Configuration**.



Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: direct input of information specific to the measuring point, such as the measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Accessories

The accessories currently available for the product can be selected at www.endress.com:


1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Spare parts & Accessories**.

Online tools

Product information about the entire life cycle of the device is available at:
www.endress.com/onlinetools

Documentation

The following document types are available in the Downloads area of the Endress+Hauser website (www.endress.com/downloads), depending on the device version:

Document type	Purpose and content of the document
Technical Information (TI)	Planning aid for your device The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.
Brief Operating Instructions (KA)	Guide that takes you quickly to the 1st measured value The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning.
Operating Instructions (BA)	Your reference document The Operating Instructions contain all the information that is required in various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal.
Description of Device Parameters (GP)	Reference for your parameters The document provides a detailed explanation of each individual parameter. The description is aimed at those who work with the device over the entire life cycle and perform specific configurations.
Safety instructions (XA)	Depending on the approval, safety instructions for electrical equipment in hazardous areas are also supplied with the device. These are an integral part of the Operating Instructions.  The nameplate indicates which Safety Instructions (XA) apply to the device.
Supplementary device-dependent documentation (SD/FY)	Always comply strictly with the instructions in the relevant supplementary documentation. The supplementary documentation is a constituent part of the device documentation.



www.addresses.endress.com
