

# Safety Instructions

## Proline Promass 300

Class I, Zone 1 or Zone 0/1  
Zone 21



---

# Proline Promass 300

## Table of contents

About this document ..... 4

Associated documentation ..... 4

Certificates and declarations ..... 5

Manufacturer address ..... 5

Extended order code ..... 5

Safety instructions: General ..... 9

Safety instructions: Installation ..... 11

Safety instructions: EPL Ga (Zone 0) ..... 14

Safety instructions: Zone 21 ..... 14

Temperature tables ..... 14

Explosion hazards arising from gas and dust ..... 25

Connection values: Signal circuits ..... 27

About this document

 The document number of these Safety Instructions (XA) must match the information on the nameplate.

Associated documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

- *Device Viewer* ([www.endress.com/deviceviewer](http://www.endress.com/deviceviewer)): Enter serial number from nameplate.
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

To commission the device, please observe the Operating Instructions pertaining to the device:

| Measuring instrument | Documentation code |                     |             |             |              |
|----------------------|--------------------|---------------------|-------------|-------------|--------------|
|                      | HART               | FOUNDATION Fieldbus | PROFIBUS PA | PROFIBUS DP | Modbus RS485 |
| Promass A 300 (8A3B) | BA01482D           | BA01515D            | BA01504D    | –           | BA01493D     |
| Promass A 300 (8A3C) | BA01816D           | BA01843D            | BA01841D    | BA01857D    | BA01884D     |
| Promass E 300        | BA01484D           | BA01517D            | BA01506D    | BA01855D    | BA01495D     |
| Promass F 300        | BA01485D           | BA01518D            | BA01507D    | BA01850D    | BA01496D     |
| Promass H 300        | BA01486D           | BA01519D            | BA01508D    | BA01858D    | BA01497D     |
| Promass I 300        | BA01487D           | BA01520D            | BA01509D    | BA01859D    | BA01498D     |
| Promass O 300        | BA01488D           | BA01521D            | BA01510D    | BA01860D    | BA01499D     |
| Promass P 300        | BA01489D           | BA01522D            | BA01511D    | BA01861D    | BA01500D     |
| Promass Q 300        | BA01490D           | BA01523D            | BA01512D    | BA01862D    | BA01501D     |
| Promass S 300        | BA01491D           | BA01524D            | BA01513D    | BA01863D    | BA01502D     |
| Promass X 300        | BA01492D           | BA01525D            | BA01514D    | BA01864D    | BA01503D     |

| Measuring instrument | Documentation code |          |                            |            |
|----------------------|--------------------|----------|----------------------------|------------|
|                      | EtherNet/IP        | PROFINET | PROFINET over Ethernet-APL | Modbus TCP |
| Promass A 300 (8A3B) | BA01699D           | BA01736D | –                          | –          |
| Promass A 300 (8A3C) | BA01842D           | BA01840D | BA02108D                   | BA02401D   |
| Promass E 300        | BA01727D           | BA01738D | BA02110D                   | BA02403D   |
| Promass F 300        | BA01728D           | BA01739D | BA01739D                   | BA02404D   |
| Promass H 300        | BA01729D           | BA01740D | BA02111D                   | BA02405D   |
| Promass I 300        | BA01730D           | BA01741D | BA02112D                   | BA02406D   |
| Promass O 300        | BA01731D           | BA01742D | BA02113D                   | BA02407D   |

| Measuring instrument | Documentation code |          |                            |            |
|----------------------|--------------------|----------|----------------------------|------------|
|                      | EtherNet/IP        | PROFINET | PROFINET over Ethernet-APL | Modbus TCP |
| Promass P 300        | BA01732D           | BA01743D | BA02114D                   | BA02408D   |
| Promass Q 300        | BA01733D           | BA01744D | BA02116D                   | BA02409D   |
| Promass S 300        | BA01734D           | BA01745D | BA02117D                   | BA02410D   |
| Promass X 300        | BA01735D           | BA01746D | BA02118D                   | BA02411D   |

Additional documentation

| Contents                                   | Document type                                               | Documentation code          |
|--------------------------------------------|-------------------------------------------------------------|-----------------------------|
| Remote display and operating module DKX001 | Special documentation                                       | SD01763D                    |
|                                            | Safety Instructions<br>Zone 1, Zone 21; Class I, Division 1 | XA01499D                    |
| Explosion Protection                       | Brochure                                                    | CP00021Z/11                 |
| Ethernet-APL Installation Drawing          | Installation Drawing                                        | HE_01622                    |
| Control drawing                            |                                                             | As wanted on the nameplate. |

Please note the documentation associated with the device.

Certificates and declarations

Certificate number  
CSA 16.70087366

Notified body  
CSA Group


Manufacturer address

Endress+Hauser Flowtec AG  
Kägenstrasse 7  
4153 Reinach BL  
Switzerland

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code



Device type

The device and the device design is defined in the "Device type" section (Product root).

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Device type

| Position | Order code for    | Selected option                                                 | Description                                  |
|----------|-------------------|-----------------------------------------------------------------|----------------------------------------------|
| 1        | Instrument family | 8                                                               | Coriolis flowmeter                           |
| 2        | Sensor            | A, E, F, H, I, O, P, Q, S, X <sup>1)</sup>                      | Sensor type                                  |
| 3        | Transmitter       | 3                                                               | Transmitter type:<br>4-wire, compact version |
| 4        | Generation index  | B, C                                                            | Platform generation                          |
| 5, 6     | Nominal diameter  | Examples:<br>02, 04, 40, 50, 1H, 3E <sup>2)</sup> <sup>3)</sup> | Nominal diameter of sensor                   |

- 1) For replacement transmitter only: X
- 2) For the exact specification of the nominal diameter, see nameplate
- 3) For replacement transmitter only: XX

Basic specifications

| Position 1, 2<br>Order code for "Approval"<br>Selected option | Position 4, 5<br>Order code for "Output, input 1"<br>Selected option | Type of protection                                                                                                   |
|---------------------------------------------------------------|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|
| C1                                                            | BA, BB, GA, LA, MA, MB, NA, RA, RB, SA                               | CL.I, Zone 0/1, AEx/Ex db eb ia IIB T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb IIIC T** °C Db                 |
|                                                               | CA, CC, HA, MC, RC, TA                                               | CL.I, Zone 0/1, AEx/Ex db eb ia [ia Ga] IIB T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db |
| C2                                                            | BA, BB, GA, LA, NA, MA, MB, RA, RB, SA,                              | CL.I, Zone 0/1, AEx/Ex db eb ia IIC T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb IIIC T** °C Db                 |
|                                                               | CA, CC, HA, MC, RC, TA                                               | CL.I, Zone 0/1, AEx/Ex db eb ia [ia Ga] IIC T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db |
| C3                                                            | BA, BB, GA, LA, MA, MB, NA, RA, RB, SA                               | CL.I, Zone 0/1, AEx/Ex db ia IIB T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb IIIC T** °C Db                    |
|                                                               | CA, CC, HA, MC, RC, TA                                               | CL.I, Zone 0/1, AEx/Ex db ia [ia Ga] IIB T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db    |
| C4                                                            | BA, BB, GA, LA, MB, NA, RA, RB, SA, MA                               | CL.I, Zone 0/1, AEx/Ex db ia IIC T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb IIIC T** °C Db                    |
|                                                               | CA, CC, HA, MC, RC, TA                                               | CL.I, Zone 0/1, AEx/Ex db ia [ia Ga] IIC T6...T1 Ga/Gb <sup>1)</sup><br>Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db    |

1) Sensors Promass A DN 1, Promass H DN 8 to 50, Promass I DN 8 to 80 are only suitable for Class I, Zone 1, equipment protection level EPL Gb.

| Position | Order code for  | Selected option | Description                                  |
|----------|-----------------|-----------------|----------------------------------------------|
| 4, 5     | Output; input 1 | BA              | 4-20mA HART                                  |
|          |                 | CA              | 4-20mA HART Ex-i passive                     |
|          |                 | CC              | 4-20mA HART Ex-i active                      |
|          |                 | GA              | PROFIBUS PA                                  |
|          |                 | HA              | PROFIBUS PA Ex-i                             |
|          |                 | LA              | PROFIBUS DP                                  |
|          |                 | MA              | Modbus RS485                                 |
|          |                 | MB              | Modbus TCP over Ethernet-APL/SPE, 10Mbit/s   |
|          |                 | MC              | Modbus TCP over Ethernet-APL, Ex-i, 10Mbit/s |
|          |                 | NA              | EtherNet/IP 2-port switch integrated         |
|          |                 | RA              | PROFINET IO 2-port switch integrated         |
|          |                 | RB              | PROFINET over Ethernet-APL/SPE, 10Mbit/s     |
|          |                 | RC              | PROFINET over Ethernet-APL, Ex-i, 10Mbit/s   |

| Position | Order code for                           | Selected option | Description                                                                                                 |
|----------|------------------------------------------|-----------------|-------------------------------------------------------------------------------------------------------------|
| 6        | Output; input 2                          | SA              | FOUNDATION Fieldbus                                                                                         |
|          |                                          | TA              | FOUNDATION Fieldbus Ex-i                                                                                    |
|          |                                          | A               | W/o                                                                                                         |
|          |                                          | B               | 4-20mA                                                                                                      |
|          |                                          | C               | 4-20mA Ex-i passive                                                                                         |
|          |                                          | D               | Configurable I/O initial setting off                                                                        |
|          |                                          | E               | Pulse/frequency/switch output                                                                               |
|          |                                          | F               | Pulse output, phase-shifted                                                                                 |
|          |                                          | G               | Pulse/frequency/switch output Ex-i passive                                                                  |
|          |                                          | H               | Relay                                                                                                       |
|          |                                          | I               | 4-20mA input                                                                                                |
|          |                                          | J               | Status input                                                                                                |
| 7        | Output; input 3                          | A               | W/o                                                                                                         |
|          |                                          | B               | 4-20mA                                                                                                      |
|          |                                          | C               | 4-20mA Ex-i passive                                                                                         |
|          |                                          | D               | Configurable I/O initial setting off                                                                        |
|          |                                          | E               | Pulse/frequency/switch output                                                                               |
|          |                                          | F               | Pulse output, phase-shifted                                                                                 |
|          |                                          | G               | Pulse/frequency/switch output Ex-i passive                                                                  |
|          |                                          | H               | Relay                                                                                                       |
|          |                                          | I               | 4-20mA input                                                                                                |
|          |                                          | J               | Status input                                                                                                |
| 8        | Display; Operation                       | A               | W/o; via communication                                                                                      |
|          |                                          | F               | 4-line, illuminated; touch control                                                                          |
|          |                                          | G               | 4-line, illuminated; touch control + WLAN                                                                   |
|          |                                          | M               | Without; prepared for remote display DKX001 <sup>1)</sup>                                                   |
|          |                                          | O               | Separate, with remote display DKX001 <sup>1)</sup> , 4-line, illuminated; 10 m / 30 ft cable; touch control |
| 9        | Housing                                  | A               | Alu, coated                                                                                                 |
|          |                                          | L               | Cast, stainless                                                                                             |
| 11, 12   | Meas. Tube Mat.,<br>Wetted Parts Surface | LA              | Stainl. steel, cryogenic -196°C/-320°F                                                                      |

| Position | Order code for | Selected option | Description |
|----------|----------------|-----------------|-------------|
| 17, 18   | Device Model   | A1              | 1           |
|          |                | A2              | 2           |

1) DKX001 is separately approved.

### Optional specifications

| ID | Order code for       | Selected option | Description                                                       |
|----|----------------------|-----------------|-------------------------------------------------------------------|
| Cx | Sensor option        | CA              | Rupture disk                                                      |
| Cx | Sensor option        | CG              | Extended neck for insulation                                      |
| Cx | Sensor option        | CH              | Purge connection                                                  |
| Jx | Test, certificate    | JP              | Ambient temperature measuring device –50 °C                       |
| Px | Enclosed accessories | P8              | Wireless antenna, wide area (external WLAN antenna) <sup>1)</sup> |

1) The external WLAN antenna is available with the order code for "Accessory Enclosed", option P8.

### Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations or guidelines (e.g. CEC or NEC)
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Use the device only in media where the wetted materials are known to be suitable.
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application, and the temperature classes.
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- An additional assessment must be conducted to confirm that the device is suitable for installation in hybrid mixtures (explosive gas and dust occurring simultaneously).

- Only open the cover of the AEx/Ex db transmitter housing if one of the following conditions is met:
  - An explosive atmosphere is not present.
  - A waiting time of 10 minutes is observed after switching off the power supply.  
The following warning notice is on the device:  
WARNING – AFTER DE-ENERGIZING, DELAY 10 MINUTES  
BEFORE OPENING ENCLOSURE IN TYPE OF PROTECTION EX D
- In devices with damaged AEx/Ex db threads:
  - Use in hazardous areas is not permitted.
  - Repair of AEx/Ex db threads is not permitted.
- Observe all the technical data of the device (see nameplate).
- Avoid electrostatic charges which could result in electrostatic discharges while installing, operating, cleaning or maintaining:
  - For external non-metallic surfaces, e.g. housing, attached additional plates, RFID tag.
  - For attached external metallic parts that are not integrated into the local potential equalization system, e.g. nameplate tag, RFID tag.
  - Do not use in areas where the devices/electronic housing are exposed to highly charge-generating processes, pneumatically conveyed dusts and/or charge spraying in an electrostatic coating process.
  - Do not rub surfaces dry. Clean only with moist cloth.
  - Information on electrostatic hazards and how to minimize the generation of static electricity can be found in the technical specification CEC or NEC.

 **WARNING**

**Substitution of components is not permitted.**

- Substitution of components may impair intrinsic safety.

## Safety instructions: Installation

### General installation instructions

- Continuous service temperature of the connecting cable:  $-40$  to  $+85$  °C ( $-50$  to  $+85$  °C for optional specification, ID Jx (Test, certificate) = JP); but at least according to the operating temperature range of the application plus allowance for process conditions ( $T_{a, \min}$  and  $T_{a, \max} + 20$  K).
- The following applies when installing the transmitter with an AEx/Ex db connection compartment:  
Only use separately certified cable glands, sealing plugs and thread adapters (AEx/Ex db IIC) that are suitable for operating temperatures from  $-40$  to  $+85$  °C ( $-50$  to  $+85$  °C for optional specification) and for IP 66/67.  
The mounted metal thread extensions and sealing plugs are tested and certified as part of the devices for the type of protection AEx/Ex db IIC. The thread extension or the sealing plug labeled as follows for identification purposes:  
d or NPTd: NPT  $\frac{1}{2}$ "
- The following applies when installing a transmitter with an AEx/Ex eb connection compartment:  
Only use separately certified cable glands, sealing plugs and thread adapters (AEx/Ex eb IIC) which are suitable for operating temperatures from  $-40$  to  $+85$  °C ( $-50$  to  $+85$  °C for optional specification) and for IP 66/67.  
The mounted metal thread extensions and sealing plugs supplied are tested and certified as part of the devices for the type of protection AEx/Ex eb IIC.  
The cables must be routed such that they are securely seated, and sufficient strain relief must be ensured.
- When the measuring device is connected, attention must be paid to the type of protection at the transmitter.
- Turning the transmitter housing
  - Loosen both hexagon socket screws until the transmitter housing can be turned.
  - Turn transmitter housing to desired position (mechanically limited); if necessary turn  $270^\circ$  in other direction.
  - Tighten both hexagon socket screws with a maximum of 7 Nm.
- For the device with order code "Output; Input 1", option MC:
  - When using Port 1 (terminal 26/27) as a 2-WISE power load APL port with the SLAA profile, Port 2 (RJ45) must not be used for Modbus TCP.
  - Parallel operation of Port 1 (terminal 26/27) and Port 2 (RJ45) is not permitted.
- Install transmitter circuit wiring, using threaded conduit or other suitable wiring methods, in accordance with the Canadian Electrical Code (CEC), Section 18, or the National Electrical Code (NEC), Articles 500–516, as applicable.

### Installation in potentially explosive atmospheres

- Do not disconnect the electrical connection of the power supply circuit when energized.
- Do not open the connection compartment cover when the device is energized.
- Exception for the device with order code "Approval; Transmitter + Sensor", options C1, C2 (AEx/Ex db eb) and "Power Supply", option D (24V) and "Output; Input 1", options CA, CB, CC, HA, MC, RC, TA (Intrinsically safe circuits): the AEx/Ex eb connection compartment of the transmitter may be opened for a short period to perform live maintenance of intrinsically safe circuits. All internal non-intrinsically safe circuits are protected by an addition IP30 rated cover.
- Exception for the device with order code "Approval; Transmitter + Sensor", options C1, C2 (AEx/Ex db eb) and "Output; Input 1", options CA, CB, CC, HA, MC, RC, TA (Intrinsically safe circuits): Transmitters with AEx/Ex db eb may only be connected to or operated with the service interface (Port 2, RJ45) if they are part of an Ex i (intrinsically safe) circuit.  
In all other configurations, connection to or operation with Port 2 is not permitted.

### Use of cable glands, sealing plugs and thread adapters

- Only use Ex certified cable glands, sealing plugs and thread adapters that are suitable for the intended application (see nameplates).
- Plastic sealing plugs are mounted to cable entries and metallic thread extensions for temporary protection during transport and storage. These must be replaced with suitable Ex certified cable entry devices for permanent use.
- The mounted metallic thread extensions and sealing plugs are tested and certified as part of the device. These meet the device's specific requirements.
- Supplied Ex cable glands are separately certified and meet the device's specific requirements.
- All unused cable entries must be closed with suitable Ex certified sealing plugs.
- Observe selection criteria for Ex cable entry devices as per CEC or NEC.

### Optional external WLAN antenna

- The external WLAN antenna (with or without extension cable) and the antenna feedthrough can only be installed in devices with an AEx/Ex eb connection compartment. Using them with an connection compartment is not permitted.
- Use only the external antenna (with or without extension cable) and the antenna feedthrough supplied by Endress+Hauser.
- The antenna feedthrough must be mounted to the transmitter with a tightening torque of 4 Nm.
- Use only an external antenna (with or without extension cable) equipped with a Type-N male connector (MIL-STD-348).
- The coupling nut of the Type-N male connector must be tightened by hand only.

### Optional RFID TAG

- Do not use in areas with high electromagnetic field intensities.
- Avoid electrostatic charging.
- Ensure sufficient distance from processes generating high charges.

### Intrinsic safety

- Observe the guidelines for interconnecting intrinsically safe circuits (e.g. CEC or NEC as applicable , proof of intrinsic safety).
- The device's intrinsically safe input/output circuits are rated AEx/Ex ia IIC Ga. When connected to certified intrinsically safe apparatus with an AEx/Ex ib IIC Gb or AEx/Ex ib IIB Gb rating, the level of protection of the overall system becomes AEx/Ex ib IIC Gb or AEx/Ex ib IIB Gb , respectively.
- The device's intrinsically safe output circuit for remote display is rated AEx/Ex ia IIC Ga. When connected to the remote display and operating module DKX001, which is rated AEx/Ex ia IIC Gb the level of protection of the overall system becomes AEx/Ex ia IIC Gb.

### Remote display and operating module DKX001

- When using the remote display and operating module DKX001 the internal display and operating module must be removed.
- When connected to a separately ordered remote display and operating module DKX001, use only the following variants: Basic specification of the remote display and operating module DKX001, order code "Approval", option CI
- Observe additional instructions in the Safety Instructions (XA) of the remote display and operating module DKX001.

### Potential equalization

- The device must be connected to the potential equalization system using designated protective ground terminals.
- It is also possible to integrate the device into the potential equalization system through a pipe system, provided that the pipe system meets the grounding requirements of applicable national regulations.

#### Safety instructions: EPL Ga (Zone 0)

Install the transmitter electronics in Zone 1. For sensors with EPL Ga/Gb (Zone 0/1), the EPL Ga (Zone 0) is only permitted in the measuring tube.

#### Safety instructions: Zone 21

- The enclosure may only be opened for brief maintenance or inspection activities where the area is confirmed to be free of combustible dust. Suitable precautions must be taken during this time to prevent dust entering the electronic compartment.
- Seal unused entry glands with approved blanking elements that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- Only use certified cable entries and blanking elements. The metal cable entries, extensions and sealing plugs supplied meet this requirement.
- Only use separately certified cable glands, sealing plugs and thread adapters (AEx/Ex tb IIIC) which are suitable for operating temperatures from  $-40$  to  $+85$  °C ( $-50$  to  $+85$  °C for optional specification) and for IP 66/67.  
The mounted metallic thread extensions and metallic sealing plugs are tested and certified as part of the devices for the type of protection AEx/Ex tb IIIC.
- The device's intrinsically safe output circuit for remote display is rated AEx/Ex ia IIIC Da. When connected to the remote display and operating module DKX001, which is rated AEx/Ex ia IIIC Db, the level of protection of the overall system becomes AEx/Ex ia IIIC Db.  
Connection values: Signal circuits, DKX001 →  29

#### Temperature tables

##### Minimum ambient temperature

- $T_{a, \min} = -40$  °C
- *Optional specification, ID Jx (Test, Certificate) = JP*  
 $T_{a, \min} = -50$  °C depending on the selected device variant (see nameplate)

Maximum ambient temperature

T<sub>a, max</sub> = +60 °C depending on temperature class, maximum medium temperature and device-specific features. See the corresponding temperature tables.

Minimum medium temperature

- Promass A, F, H, I, P, Q, S, X:  
T<sub>m, min</sub> = -50 °C
- Promass E, O:  
T<sub>m, min</sub> = -40 °C
- Promass F, Q with cryogenic temperature version (order code for "Measuring tube material", option LA):  
T<sub>m, min</sub> = -196 °C

Maximum medium temperature without thermal insulation

NOTICE

In case of heating, risk of overheating.

- ▶ On devices with Heating jacket the corresponding temperature tables for devices with thermal insulation, are to be observed.
- ▶ Make sure that the heating medium, may not exceeded the maximum specified medium temperature of the exact used temperature classes of the device.

( ) = The maximum permitted medium temperatures in brackets only apply if the sensor is installed in such a way that the transmitter is not mounted above the sensor and free convection can occur on all sides.

Promass A (8A3B\*\*-\*, 8A3C\*\*-\*)

| DN     | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|--------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|        |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 1 to 4 | 205                               | 50                          | 50                       | 95             | 130            | 150            | 205            | 205            |
|        |                                   | 60                          | –                        | 95             | 130            | 150            | 205            | 205            |

Promass E

| DN      | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|---------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|         |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8 to 50 | 150                               | 50                          | 50                       | 100            | 130            | 130            | 150            | 150            |
|         |                                   | 55                          | –                        | 80             | 100            | 130            | 150            | 150            |
|         |                                   | 60                          | –                        | (80)           | (100)          | (130)          | (150)          | (150)          |
| 80      | 150                               | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |

| DN | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|    |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
|    |                                   | 55                          | –                        | 75             | 110            | 150            | 150            | 150            |
|    |                                   | 60                          | –                        | (75)           | (110)          | (150)          | (150)          | (150)          |

Promass F

| DN        | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|           |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 08 to 15  | 150                                             | 50                          | 50                       | 95             | 130            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 95             | 130            | 150            | 150            | 150            |
|           | 150 <sup>2)</sup>                               | 50                          | 50                       | 95             | 100            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 95             | 100            | 150            | 150            | 150            |
|           | 240                                             | 50                          | 50                       | 95             | 130            | 160            | 240            | 240            |
|           |                                                 | 60                          | –                        | 95             | 130            | 160            | (240)          | (240)          |
| 15 to 25  | 350                                             | 50                          | 45                       | 95             | 130            | 175            | 275            | 350            |
|           |                                                 | 60                          | –                        | 95             | 130            | 175            | 275            | 350            |
| 25 to 50  | 150                                             | 50                          | 50                       | 95             | 130            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 95             | 130            | 150            | 150            | 150            |
|           | 150 <sup>2)</sup>                               | 50                          | 50                       | 95             | 100            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 95             | 100            | 150            | 150            | 150            |
|           | 240                                             | 50                          | 50                       | 95             | 130            | 160            | 240            | 240            |
|           |                                                 | 60                          | –                        | 95             | 130            | 160            | (240)          | (240)          |
| 80 to 250 | 150                                             | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 75             | 110            | 150            | 150            | 150            |
|           | 150 <sup>2)</sup>                               | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 75             | 110            | 150            | 150            | 150            |
|           | 240                                             | 50                          | 50                       | 75             | 110            | 170            | 240            | 240            |
|           |                                                 | 60                          | –                        | 75             | 110            | 170            | (240)          | (240)          |
| 50 to 250 | 350                                             | 50                          | 45                       | 85             | 120            | 175            | 275            | 350            |
|           |                                                 | 60                          | –                        | 85             | 120            | 175            | 275            | 350            |

1) Maximum temperature range, see nameplate  
2) Cryogenic temperature version: T<sub>m</sub> = -196 to 150 °C

Promass H

| DN       | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|          |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8        | 150                                             | 50                          | 50                       | 65             | 100            | 150            | 150            | 150            |
|          |                                                 | 60                          | –                        | 65             | 100            | 150            | 150            | 150            |
| 8        | 205                                             | 50                          | 50                       | 65             | 100            | 160            | 205            | 205            |
|          |                                                 | 60                          | –                        | 65             | 100            | 160            | 205            | 205            |
| 15 to 50 | 150                                             | 50                          | 50                       | 75             | 115            | 150            | 150            | 150            |
|          |                                                 | 60                          | –                        | 75             | 115            | 150            | 150            | 150            |
| 15 to 50 | 205                                             | 50                          | 50                       | 75             | 115            | 180            | 205            | 205            |
|          |                                                 | 60                          | –                        | 75             | 115            | 180            | 205            | 205            |

1) Maximum temperature range, see nameplate

Promass I

| DN                    | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------------------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|                       |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8, 15,<br>15FB, 25    | 150                               | 50                          | 50                       | 95             | 130            | 150            | 150            | 150            |
|                       |                                   | 60                          | –                        | 95             | 120            | (150)          | (150)          | (150)          |
| 25FB, 40,<br>40FB, 50 | 150                               | 50                          | 50                       | 85             | 120            | 150            | 150            | 150            |
|                       |                                   | 60                          | –                        | 85             | 120            | (150)          | (150)          | (150)          |
| 50FB, 80              | 150                               | 50                          | 50                       | 85             | 120            | 150            | 150            | 150            |
|                       |                                   | 60                          | –                        | 85             | 120            | (150)          | (150)          | (150)          |
| FB = Full bore        |                                   |                             |                          |                |                |                |                |                |

Promass O

| DN        | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|           |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 80 to 250 | 205                               | 50                          | 50                       | 75             | 110            | 170            | 205            | 205            |
|           |                                   | 55                          | –                        | 75             | 110            | 170            | 205            | 205            |
|           |                                   | 60                          | –                        | 75             | 110            | 170            | (205)          | (205)          |

Promass P

| DN       | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|          |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8        | 150                                             | 45                          | 45                       | 65             | 100            | 150            | 150            | 150            |
|          |                                                 | 60                          | –                        | 65             | 100            | 150            | 150            | 150            |
|          | 205                                             | 45                          | 45                       | 65             | 100            | 160            | 205            | 205            |
|          |                                                 | 60                          | –                        | 65             | 100            | 160            | 205            | 205            |
| 15 to 50 | 150                                             | 50                          | 50                       | 75             | 115            | 150            | 150            | 150            |
|          |                                                 | 60                          | –                        | 75             | 115            | 150            | 150            | 150            |
|          | 205                                             | 50                          | 50                       | 75             | 115            | 180            | 205            | 205            |
|          |                                                 | 60                          | –                        | 75             | 115            | 180            | 205            | 205            |

1) Maximum temperature range, see nameplate

Promass Q

| DN        | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|           |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 25 to 250 | 205                                             | 50                          | 50                       | 75             | 110            | 160            | 205            | 205            |
|           |                                                 | 60                          | –                        | 75             | 110            | 160            | 205            | 205            |
| 25 to 250 | 150 <sup>2)</sup>                               | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 75             | 110            | 150            | 150            | 150            |

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: T<sub>m</sub> = –196 to 150 °C

Promass S

| DN       | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|          |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8        | 150                               | 45                          | 45                       | 65             | 100            | 150            | 150            | 150            |
|          |                                   | 60                          | –                        | 65             | 100            | 150            | 150            | 150            |
| 15 to 50 | 150                               | 50                          | 50                       | 75             | 115            | 150            | 150            | 150            |
|          |                                   | 60                          | –                        | 75             | 115            | 150            | 150            | 150            |

Promass X

| DN  | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|     |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 350 | 180                               | 50                          | 50                       | 90             | 120            | 170            | 180            | 180            |
|     |                                   | 55                          | –                        | 90             | 120            | 170            | 180            | 180            |
|     |                                   | 60                          | –                        | (90)           | (120)          | (170)          | (180)          | (180)          |

Maximum medium temperature with thermal insulation according to Endress+Hauser specifications

NOTICE

In case of heating, risk of overheating.

- ▶ On devices with Heating jacket the corresponding temperature tables for devices with thermal insulation, are to be observed.
- ▶ Make sure that the heating medium, may not exceeded the maximum specified medium temperature of the exact used temperature classes of the device.

 For information on the thermal insulation of the device, see the "Thermal insulation" section of the "Operating instructions" document .

( ) = The maximum permitted medium temperatures in brackets only apply if the sensor is installed in such a way that the transmitter is not mounted above the sensor and free convection can occur on all sides.

Promass A (8A3B\*\*-\*, 8A3C\*\*-\*...)

| DN     | T <sub>m, max range</sub> [°C] | T <sub>a, max</sub> [°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|--------|--------------------------------|--------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|        |                                |                          | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 1 to 4 | 205                            | 50                       | 50                       | 95             | 130            | 150            | 205            | 205            |
|        |                                | 55                       | –                        | (95)           | (130)          | (150)          | (205)          | (205)          |

Promass E

| DN      | T <sub>m, max range</sub> [°C] | T <sub>a, max</sub> [°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|---------|--------------------------------|--------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|         |                                |                          | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8 to 50 | 150                            | 50                       | 50                       | 100            | 130            | 130            | 150            | 150            |
|         |                                | 55                       | –                        | (100)          | (130)          | (130)          | (150)          | (150)          |
| 80      | 150                            | 45                       | 50                       | 75             | 110            | 150            | 150            | 150            |
|         |                                | 50                       | –                        | 75             | 110            | 150            | 150            | 150            |
|         |                                | 55                       | –                        | (75)           | (110)          | (150)          | (150)          | (150)          |

Promass F

| DN       | T <sub>m, max range</sub> <sup>1)</sup> [°C] | T <sub>a, max</sub> [°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----------|----------------------------------------------|--------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|          |                                              |                          | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 08 to 15 | 150                                          | 50                       | 50                       | 95             | 130            | 150            | 150            | 150            |
|          |                                              | 60                       | –                        | 95             | 110            | (150)          | (150)          | (150)          |

| DN        | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|           |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
|           | 150 <sup>2)</sup>                               | 50                          | 50                       | 95             | 130            | 150            | 150            | 150            |
|           |                                                 | 55                          | –                        | 95             | (130)          | (150)          | (150)          | (150)          |
|           |                                                 | 60                          | –                        | 95             | 110            | 110            | 110            | 110            |
|           | 240                                             | 50                          | 50                       | 95             | 130            | 160            | 240            | 240            |
|           |                                                 | 55                          | –                        | 95             | (130)          | (160)          | (240)          | (240)          |
|           |                                                 | 60                          | –                        | 95             | 110            | 110            | 110            | 110            |
| 15 to 25  | 350                                             | 50                          | 45                       | 95             | 130            | 175            | 275            | 350            |
|           |                                                 | 60                          | –                        | 95             | 130            | 175            | 275            | 350            |
| 25 to 50  | 150                                             | 50                          | 50                       | 95             | 130            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 95             | 110            | (150)          | (150)          | (150)          |
|           | 150 <sup>2)</sup>                               | 50                          | 50                       | 95             | 130            | 150            | 150            | 150            |
|           |                                                 | 55                          | –                        | 95             | (130)          | (150)          | (150)          | (150)          |
|           |                                                 | 60                          | –                        | 95             | 110            | 110            | 110            | 110            |
|           | 240                                             | 50                          | 50                       | 95             | 130            | 160            | 240            | 240            |
|           |                                                 | 55                          | –                        | 95             | (130)          | (160)          | (240)          | (240)          |
|           |                                                 | 60                          | –                        | 95             | 110            | 110            | 110            | 110            |
|           | 150 <sup>2)</sup>                               | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 75             | 110            | (150)          | (150)          | (150)          |
| 80 to 250 | 150                                             | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 75             | 110            | (150)          | (150)          | (150)          |
|           |                                                 | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |
|           | 150 <sup>2)</sup>                               | 55                          | –                        | 75             | 110            | 150            | 150            | 150            |
|           |                                                 | 60                          | –                        | 75             | 110            | 110            | 110            | 110            |
|           | 240                                             | 50                          | 50                       | 75             | 110            | 170            | 240            | 240            |
|           |                                                 | 55                          | –                        | 75             | 110            | (170)          | (240)          | (240)          |
|           |                                                 | 60                          | –                        | 75             | 110            | 110            | 110            | 110            |
|           | 240                                             | 50                          | 50                       | 75             | 110            | 170            | 240            | 240            |
|           |                                                 | 55                          | –                        | 75             | 110            | (170)          | (240)          | (240)          |
|           |                                                 | 60                          | –                        | 75             | 110            | 110            | 110            | 110            |
| 50 to 250 | 350                                             | 50                          | 45                       | 85             | 120            | 175            | 275            | 350            |
|           |                                                 | 60                          | –                        | 85             | 120            | 175            | 275            | 350            |

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: T<sub>m</sub> = –196 to 150 °C

Promass H

| DN       | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|          |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8        | 150                                             | 50                          | 50                       | 65             | 100            | 150            | 150            | 150            |
|          |                                                 | 55                          | –                        | 65             | 100            | (150)          | (150)          | (150)          |
|          |                                                 | 60                          | –                        | 65             | 100            | 100            | 100            | 100            |
| 8        | 205                                             | 50                          | 50                       | 65             | 100            | 160            | 205            | 205            |
|          |                                                 | 55                          | –                        | 65             | 100            | (160)          | (205)          | (205)          |
|          |                                                 | 60                          | –                        | 65             | 100            | 100            | 100            | 100            |
| 15 to 50 | 150                                             | 50                          | 50                       | 75             | 115            | 150            | 150            | 150            |
|          |                                                 | 55                          | –                        | 75             | 115            | (150)          | (150)          | (150)          |
|          |                                                 | 60                          | –                        | 75             | 115            | 115            | 115            | 115            |
| 15 to 50 | 205                                             | 50                          | 50                       | 75             | 115            | 180            | 205            | 205            |
|          |                                                 | 55                          | –                        | 75             | 115            | (180)          | (205)          | (205)          |
|          |                                                 | 60                          | –                        | 75             | 115            | 115            | 115            | 115            |

1) Maximum temperature range, see nameplate

Promass I

| DN                    | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------------------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|                       |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8, 15,<br>15FB, 25    | 150                               | 50                          | 50                       | 95             | 130            | 150            | 150            | 150            |
|                       |                                   | 60                          | –                        | 95             | 120            | (150)          | (150)          | (150)          |
| 25FB, 40,<br>40FB, 50 | 150                               | 50                          | 50                       | 85             | 120            | 150            | 150            | 150            |
|                       |                                   | 60                          | –                        | 85             | 120            | (150)          | (150)          | (150)          |
| 50FB, 80              | 150                               | 50                          | 50                       | 85             | 120            | 150            | 150            | 150            |
|                       |                                   | 60                          | –                        | 85             | 120            | (150)          | (150)          | (150)          |
| FB = Full bore        |                                   |                             |                          |                |                |                |                |                |

*Promass O*

| DN        | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|           |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 80 to 250 | 205                               | 50                          | 50                       | 75             | 110            | 170            | 205            | 205            |
|           |                                   | 55                          | –                        | (75)           | (110)          | (170)          | (205)          | (205)          |

*Promass P*

| DN       | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|          |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8        | 150                                             | 45                          | 45                       | 65             | 100            | 150            | 150            | 150            |
|          |                                                 | 50                          | –                        | 65             | 100            | 150            | 150            | 150            |
|          |                                                 | 60                          | –                        | 65             | 100            | 125            | (150)          | (150)          |
|          | 205                                             | 45                          | 45                       | 65             | 100            | 160            | 205            | 205            |
|          |                                                 | 50                          | –                        | 65             | 100            | 160            | 205            | 205            |
|          |                                                 | 60                          | –                        | 65             | 100            | 115            | (205)          | (205)          |
| 15 to 50 | 150                                             | 50                          | 50                       | 75             | 115            | 150            | 150            | 150            |
|          |                                                 | 60                          | –                        | 75             | 115            | 125            | (150)          | (150)          |
|          | 205                                             | 50                          | 50                       | 75             | 115            | 180            | 205            | 205            |
|          |                                                 | 60                          | –                        | 75             | 115            | (150)          | (150)          | (150)          |

1) Maximum temperature range, see nameplate

*Promass Q*

| DN        | T <sub>m, max range</sub> <sup>1)</sup><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----------|-------------------------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|           |                                                 |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 25 to 250 | 205                                             | 50                          | 50                       | 75             | 110            | 160            | 205            | 205            |
|           |                                                 | 55                          | –                        | (75)           | (110)          | (160)          | (205)          | (205)          |
| 25 to 250 | 150 <sup>2)</sup>                               | 50                          | 50                       | 75             | 110            | 150            | 150            | 150            |
|           |                                                 | 55                          | –                        | (75)           | (110)          | (150)          | (150)          | (150)          |

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: T<sub>m</sub> = –196 to 150 °C

Promass S


| DN       | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|----------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|          |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 8        | 150                               | 45                          | 45                       | 65             | 100            | 150            | 150            | 150            |
|          |                                   | 50                          | –                        | 65             | 100            | 150            | 150            | 150            |
|          |                                   | 60                          | –                        | 65             | 100            | 125            | (150)          | (150)          |
| 15 to 50 | 150                               | 50                          | 50                       | 75             | 115            | 150            | 150            | 150            |
|          |                                   | 60                          | –                        | 75             | 115            | 125            | (150)          | (150)          |

Promass X

| DN  | T <sub>m, max range</sub><br>[°C] | T <sub>a, max</sub><br>[°C] | T <sub>m, max</sub> [°C] |                |                |                |                |                |
|-----|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
|     |                                   |                             | T6<br>[85 °C]            | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
| 350 | 180                               | 50                          | 50                       | 90             | 120            | 170            | 180            | 180            |
|     |                                   | 55                          | –                        | (90)           | (120)          | (170)          | (180)          | (180)          |

**Maximum medium temperature for devices with thermal insulation  
NOT in accordance with Endress+Hauser specifications**

The specified reference temperature  $T_{ref}$  and the maximum medium temperature  $T_{m, max}$  for each temperature class must not be exceeded.  
→  20



A0031198

 1    *Position of reference point for temperature measurement*

- A    *Standard version*
- B    *Extended temperature version, cryogenic temperature version, high-temperature version*
- 1    *Reference point ( $T_{ref}$ )*

*Reference temperature  $T_{ref}$*

| T6<br>[85 °C] | T5<br>[100 °C] | T4<br>[135 °C] | T3<br>[200 °C] | T2<br>[300 °C] | T1<br>[450 °C] |
|---------------|----------------|----------------|----------------|----------------|----------------|
| 59            | 72             | 75             | 76             | 77             | 77             |

**Explosion hazards  
arising from gas  
and dust**

**Determining the temperature class and surface temperature with  
the temperature table**

- In the case of gas: Determine the temperature class as a function of the maximum ambient temperature  $T_{a, max}$  and the maximum medium temperature  $T_{m, max}$ .
- In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature  $T_{a, max}$  and the maximum medium temperature  $T_{m, max}$ .

**Example**

- Measured maximum ambient temperature:  $T_{a, max} = 47\text{ °C}$
- Measured maximum medium temperature:  $T_{m, max} = 108\text{ °C}$

4.

|  | Ta<br>[°C] | T6<br>[85°C] | T5<br>[100°C] | T4<br>[135°C] | T3<br>[200°C] | T2<br>[300°C] | T1<br>[450°C] |
|--|------------|--------------|---------------|---------------|---------------|---------------|---------------|
|  | 35         | 50           | 85            | 120           | 140           | 140           | 140           |
|  | 50         | -            | 85            | 120           | 140           | 140           | 140           |
|  | 60         | -            | -             | 120           | 140           | 140           | 140           |
|  | 35         | 50           | 85            | 120           | 140           | 140           | 140           |
|  | 45         | -            | 85            | 120           | 140           | 140           | 140           |
|  | 50         | -            | -             | 120           | 140           | 140           | 140           |

1.2.3.

A0031223

2 Procedure for determining the temperature class and surface temperature

1. Select device (optional).
2. In the column for the maximum ambient temperature  $T_{a, \max}$  select the temperature that is immediately greater than or equal to the maximum ambient temperature  $T_{a, \max}$  that is present.

↳  $T_{a, \max} = 50\text{ °C}$ .  
The row showing the maximum medium temperature is determined.
3. Select the maximum medium temperature  $T_{m, \max}$  of this row, which is immediately greater than or equal to the maximum medium temperature  $T_{m, \max}$  that is present.

↳ The column with the temperature class for gas is determined:  
 $108\text{ °C} \leq 120\text{ °C} \rightarrow T_4$ .
4. The maximum temperature of the temperature class determined corresponds to the maximum surface temperature for dust:  $T_4 = 135\text{ °C}$ .

Connection  
values: Signal  
circuits

The following tables contain specifications which are dependent on the transmitter type and its input and output assignment. Compare the following specifications with those on the nameplate of the transmitter.

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) |        | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) |
|------------------------------------------------------------------------|-------|----------------------------|--------|----------------|--------|----------------|--------|----------------------------------|
| 1 (+)                                                                  | 2 (-) | 26 (+)                     | 27 (-) | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                         |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                            |        |                |        |                |        |                                  |

FOUNDATION fieldbus

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) |        | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) |
|------------------------------------------------------------------------|-------|----------------------------|--------|----------------|--------|----------------|--------|----------------------------------|
| 1 (+)                                                                  | 2 (-) | 26 (A)                     | 27 (B) | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                         |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                            |        |                |        |                |        |                                  |

PROFIBUS DP

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) |        | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) |
|------------------------------------------------------------------------|-------|----------------------------|--------|----------------|--------|----------------|--------|----------------------------------|
| 1 (+)                                                                  | 2 (-) | 26 (B)                     | 27 (A) | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                         |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                            |        |                |        |                |        |                                  |

PROFIBUS PA

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) |        | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) |
|------------------------------------------------------------------------|-------|----------------------------|--------|----------------|--------|----------------|--------|----------------------------------|
| 1 (+)                                                                  | 2 (-) | 26 (B)                     | 27 (A) | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                         |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                            |        |                |        |                |        |                                  |

Modbus RS485

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) |        | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) |
|------------------------------------------------------------------------|-------|----------------------------|--------|----------------|--------|----------------|--------|----------------------------------|
| 1 (+)                                                                  | 2 (-) | 26 (B)                     | 27 (A) | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                         |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                            |        |                |        |                |        |                                  |

Modbus TCP

| Supply voltage                                                         |       | Input/output 1<br>1 (Port <sup>1)</sup> ) |        | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) <sup>1)</sup> |
|------------------------------------------------------------------------|-------|-------------------------------------------|--------|----------------|--------|----------------|--------|------------------------------------------------|
| 1 (+)                                                                  | 2 (-) | 26 (+)                                    | 27 (-) | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                                       |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                                           |        |                |        |                |        |                                                |

1) For Modbus TCP communication, either port 1 OR port 2 can be used.

PROFINET

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) <sup>1)</sup> | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) <sup>1)</sup> |
|------------------------------------------------------------------------|-------|------------------------------------------|----------------|--------|----------------|--------|------------------------------------------------|
| 1 (+)                                                                  | 2 (-) | RJ45                                     | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                                       |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                                          |                |        |                |        |                                                |

1) Port can be used for communication or as a service interface (CDI-RJ45).

PROFINET over Ethernet-APL

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) |        | Input/output 2 |        | Input/output 3 |        | Service<br>interface<br>(Port 2) <sup>1)</sup> |
|------------------------------------------------------------------------|-------|----------------------------|--------|----------------|--------|----------------|--------|------------------------------------------------|
| 1 (+)                                                                  | 2 (-) | 26 (+)                     | 27 (-) | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                                       |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                            |        |                |        |                |        |                                                |


1) No PROFINET communication available on port 2

Ethernet/IP

| Supply voltage                                                         |       | Input/output 1<br>(Port 1) <sup>1)</sup> | Input/output 2 |        | Input/output 3 |        | Service interface<br>(Port 2) <sup>1)</sup> |
|------------------------------------------------------------------------|-------|------------------------------------------|----------------|--------|----------------|--------|---------------------------------------------|
| 1 (+)                                                                  | 2 (-) | RJ45                                     | 24 (+)         | 25 (-) | 22 (+)         | 23 (-) | CDI-RJ45                                    |
| Device-specific terminal assignment: adhesive label in terminal cover. |       |                                          |                |        |                |        |                                             |

1) Port can be used for communication or as a service interface (CDI-RJ45).

Remote display and operating module DKX001



A0027518

- 1 Remote display and operating module DKX001
- 2 Protective earth (PE)
- 3 Connecting cable
- 4 Measuring device
- 5 Protective earth (PE)

Safety-related values

| Order code for<br>"Output; input 1" | Output type                    | Safety-related values                                 |                                                        |
|-------------------------------------|--------------------------------|-------------------------------------------------------|--------------------------------------------------------|
|                                     |                                | Output; input 1<br>(Port 1)                           | Service interface<br>(Port 2)                          |
| Option BA                           | Current output<br>4-20 mA HART | $U_N = 30\text{ V}_{DC}$<br>$U_M = 250\text{ V}_{AC}$ | $U_N = 3.3\text{ V}_{AC}$<br>$U_M = 250\text{ V}_{AC}$ |
| Option GA                           | PROFIBUS PA                    | $U_N = 32\text{ V}_{DC}$<br>$U_M = 250\text{ V}_{AC}$ | $U_N = 3.3\text{ V}_{AC}$<br>$U_M = 250\text{ V}_{AC}$ |
| Option LA                           | PROFIBUS DP                    | $U_N = 5\text{ V}$<br>$U_M = 250\text{ V}_{AC}$       | $U_N = 3.3\text{ V}_{AC}$<br>$U_M = 250\text{ V}_{AC}$ |

| Order code for<br>"Output; input 1" | Output type                                                                          | Safety-related values                                                                                           |                                                          |
|-------------------------------------|--------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|----------------------------------------------------------|
|                                     |                                                                                      | Output; input 1<br>(Port 1)                                                                                     | Service interface<br>(Port 2)                            |
| Option <b>MA</b>                    | Modbus RS485                                                                         | $U_N = 5 \text{ V}$<br>$U_M = 250 \text{ V}_{AC}$                                                               | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$ |
| Option <b>MB</b>                    | Modbus TCP over Ethernet-<br>APL 10 Mbit/s,<br>SPE 10 Mbit/s,<br>Ethernet 100 Mbit/s | APL port profile SLAX<br>SPE PoDL classes 10, 11, 12<br>$U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$ | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$ |
| Option <b>NA</b>                    | EtherNet/IP                                                                          | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$                                                        | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$ |
| Option <b>RA</b>                    | PROFINET                                                                             | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$                                                        | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$ |
| Option <b>RB</b>                    | PROFINET over Ethernet-<br>APL/SPE, 10Mbit/s                                         | APL port profile SLAX<br>SPE PoDL classes 10, 11, 12<br>$U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$ | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$ |
| Option <b>SA</b>                    | FOUNDATION Fieldbus                                                                  | $U_N = 32 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$                                                         | $U_N = 3.3 \text{ V}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$ |

| Order code for<br>"Output; input 2"<br>"Output; input 3" | Output type                             | Safety-related values                                                                                      |                 |
|----------------------------------------------------------|-----------------------------------------|------------------------------------------------------------------------------------------------------------|-----------------|
|                                                          |                                         | Output; input 2                                                                                            | Output; input 3 |
| Option <b>B</b>                                          | Current output<br>4-20 mA               | $U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$                                                    |                 |
| Option <b>D</b>                                          | Configurable I/O initial<br>setting off | $U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$                                                    |                 |
| Option <b>E</b>                                          | Pulse/frequency/switch<br>output        | $U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$                                                    |                 |
| Option <b>F</b>                                          | Double pulse output                     | $U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$                                                    |                 |
| Option <b>H</b>                                          | Relay output                            | $U_N = 30 \text{ V}_{DC}$<br>$I_N = 100 \text{ mA}_{DC}/500 \text{ mA}_{AC}$<br>$U_M = 250 \text{ V}_{AC}$ |                 |
| Option <b>I</b>                                          | Current input<br>4-20 mA                | $U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$                                                    |                 |
| Option <b>J</b>                                          | Status input                            | $U_N = 30 \text{ V}_{DC}$<br>$U_M = 250 \text{ V}_{AC}$                                                    |                 |

### Intrinsically safe values

| Order code for<br>"Output; input 1" | Output type                                   | Intrinsically safe values                                                                                                                                                                                                                                                                                                                         |                                                                                                                                                  |
|-------------------------------------|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
|                                     |                                               | Output; input 1<br>(Port 1)                                                                                                                                                                                                                                                                                                                       | Service interface<br>(Port 2)                                                                                                                    |
| Option CA                           | Current output<br>4-20mA HART Ex-i<br>passive | <b>Ex ia</b><br>$U_i = 30 \text{ V}$<br>$I_i = 100 \text{ mA}$<br>$P_i = 1.25 \text{ W}$<br>$L_i = 0 \text{ } \mu\text{H}$<br>$C_i = 6 \text{ nF}$                                                                                                                                                                                                | <b>Ex ia</b><br>$U_i = 10 \text{ V}$<br>$I_i = \text{n. a.}$<br>$P_i = \text{n. a.}$<br>$L_i = 0 \text{ } \mu\text{H}$<br>$C_i = 200 \text{ nF}$ |
| Option CC                           | Current output<br>4-20mA HART Ex-i<br>active  | <b>Ex ia</b><br>$U_0 = 21.8 \text{ V}$<br>$I_0 = 90 \text{ mA}$<br>$P_0 = 491 \text{ mW}$<br>$L_0 = 4.1 \text{ mH(IIC)}/15 \text{ mH(IIB)}$<br>$C_0 = 160 \text{ nF(IIC)}/1 \text{ } 160 \text{ nF(IIB)}$<br><br>$U_i = 30 \text{ V}$<br>$I_i = 10 \text{ mA}$<br>$P_i = 0.3 \text{ W}$<br>$L_i = 5 \text{ } \mu\text{H}$<br>$C_i = 6 \text{ nF}$ | <b>Ex ia</b><br>$U_i = 10 \text{ V}$<br>$I_i = \text{n. a.}$<br>$P_i = \text{n. a.}$<br>$L_i = 0 \text{ } \mu\text{H}$<br>$C_i = 200 \text{ nF}$ |
| Option HA                           | PROFIBUS PA Ex i<br>(STANDARD +<br>FISCO)     | <b>Ex ia</b><br>$U_i = 30 \text{ V}$<br>$I_i = 570 \text{ mA}$<br>$P_i = 8.5 \text{ W}$<br>$L_i = 10 \text{ } \mu\text{H}$<br>$C_i = 5 \text{ nF}$                                                                                                                                                                                                | <b>Ex ia</b><br>$U_i = 10 \text{ V}$<br>$I_i = \text{n. a.}$<br>$P_i = \text{n. a.}$<br>$L_i = 0 \text{ } \mu\text{H}$<br>$C_i = 200 \text{ nF}$ |

| Order code for<br>"Output; input 1" | Output type                                          | Intrinsically safe values                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                 |
|-------------------------------------|------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
|                                     |                                                      | Output; input 1<br>(Port 1)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | Service interface<br>(Port 2)                                                                                                                   |
| Option MC                           | Modbus TCP over<br>Ethernet-APL, Ex-i,<br>10Mbit/s   | <b>2-WISE power load, APL port profile<br/>SLAA<sup>1)</sup></b><br><b>Ex ia</b><br>$U_i = 17.5 \text{ V}$<br>$I_i = 380 \text{ mA}$<br>$P_i = 5.32 \text{ W}$<br>$L_i = 10 \text{ }\mu\text{H}$<br>$C_i = 5 \text{ nF}$<br><b>Cable specifications according to 2-WISE:</b><br>$R_c = 15 \text{ to } 150 \text{ }\Omega/\text{km}$<br>$L_c = 0.4 \text{ to } 1 \text{ mH/km}$<br>$C_c = 45 \text{ to } 200 \text{ nF/km}$<br>$C_c = C_c \text{ line/line} + 0.5 C_c \text{ line/screen}$ , if both<br>lines are floating, or<br>$C_c = C_c \text{ line/line} + C_c \text{ line/screen}$ , if the<br>screen is connected to one line<br>Length of cable (not including cable stubs):<br>$\leq 200 \text{ m (656.2 ft)}$<br>Length of cable stubs: $\leq 1 \text{ m (3.3 ft)}$ | <b>Ex ia</b><br>$U_i = 10 \text{ V}$<br>$I_i = \text{n. a.}$<br>$P_i = \text{n. a.}$<br>$L_i = 0 \text{ }\mu\text{H}$<br>$C_i = 200 \text{ nF}$ |
| Option RC                           | PROFINET over<br>Ethernet-APL, Ex-i,<br>10Mbit/s     | <b>2-WISE power load, APL port profile<br/>SLAA<sup>1)</sup></b><br><b>Ex ia</b><br>$U_i = 17.5 \text{ V}$<br>$I_i = 380 \text{ mA}$<br>$P_i = 5.32 \text{ W}$<br>$L_i = 10 \text{ }\mu\text{H}$<br>$C_i = 5 \text{ nF}$<br><b>Cable specifications according to 2-WISE:</b><br>$R_c = 15 \text{ to } 150 \text{ }\Omega/\text{km}$<br>$L_c = 0.4 \text{ to } 1 \text{ mH/km}$<br>$C_c = 45 \text{ to } 200 \text{ nF/km}$<br>$C_c = C_c \text{ line/line} + 0.5 C_c \text{ line/screen}$ , if both<br>lines are floating, or<br>$C_c = C_c \text{ line/line} + C_c \text{ line/screen}$ , if the<br>screen is connected to one line<br>Length of cable (not including cable stubs):<br>$\leq 200 \text{ m (656.2 ft)}$<br>Length of cable stubs: $\leq 1 \text{ m (3.3 ft)}$ | <b>Ex ia</b><br>$U_i = 10 \text{ V}$<br>$I_i = \text{n. a.}$<br>$P_i = \text{n. a.}$<br>$L_i = 0 \text{ }\mu\text{H}$<br>$C_i = 200 \text{ nF}$ |
| Option TA                           | FOUNDATION<br>Fieldbus Ex i<br>(STANDARD +<br>FISCO) | <b>Ex ia</b><br>$U_i = 30 \text{ V}$<br>$I_i = 570 \text{ mA}$<br>$P_i = 8.5 \text{ W}$<br>$L_i = 10 \text{ }\mu\text{H}$<br>$C_i = 5 \text{ nF}$                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | <b>Ex ia</b><br>$U_i = 10 \text{ V}$<br>$I_i = \text{n. a.}$<br>$P_i = \text{n. a.}$<br>$L_i = 0 \text{ }\mu\text{H}$<br>$C_i = 200 \text{ nF}$ |

1) For further options see Ethernet-APL Installation Drawing HE\_01622.

| Order code for<br>"Output; input 2"<br>"Output; input 3" | Output type                                   | Intrinsically safe values                                                                                       |                 |
|----------------------------------------------------------|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------|
|                                                          |                                               | Output; input 2                                                                                                 | Output; input 3 |
| Option C                                                 | Current output<br>4-20mA Ex-i passive         | <b>Ex ia</b><br>$U_i = 30\text{ V}$<br>$I_i = 100\text{ mA}$<br>$P_i = 1.25\text{ W}$<br>$L_i = 0$<br>$C_i = 0$ |                 |
| Option G                                                 | Pulse/frequency/switch<br>output Ex-i passive | <b>Ex ia</b><br>$U_i = 30\text{ V}$<br>$I_i = 100\text{ mA}$<br>$P_i = 1.25\text{ W}$<br>$L_i = 0$<br>$C_i = 0$ |                 |

**Remote display and operating module DKX001**

A connecting cable with a ratio  $L_{\text{cable}}/R_{\text{cable}} = 0.024\text{ mH}/\Omega$  and  $C_{\text{cable}} \leq 600\text{ }\mu\text{F}$  must be used when connecting the device with the remote display and operating module DKX001 or ODKX001. The connecting cable supplied by Endress+Hauser meets these requirements.

| Basic specifications<br>Position 1, 2<br>Order code for "Approval"<br>Selected option | Terminal assignment | Basic specifications<br>Position 8<br>Order code "Display; operation"<br>Option O                                    |
|---------------------------------------------------------------------------------------|---------------------|----------------------------------------------------------------------------------------------------------------------|
| Option <sup>1)</sup> C1, C2, C3, C4                                                   | 81, 82, 83, 84      | $U_0 = 3.9\text{ V}$<br>$I_0 = 1.5\text{ A}$<br>$P_0 = 600\text{ mW}$<br>$L_0 = 0$<br>$C_0 = 670\text{ }\mu\text{F}$ |

1) If the DKX001 is ordered separately: CI

---

---



71713410

[www.addresses.endress.com](http://www.addresses.endress.com)

---