

Technical Information

Cerabar PMC11, PMC21, PMP11, PMP21

Process pressure measurement

Pressure transducer with ceramic and metal sensors

Application

The Cerabar is a pressure transducer for the measurement of absolute and gauge pressure in gases, vapors, liquids and dust. The Cerabar can be used internationally thanks to a wide range of approvals and process connections.

Your benefits

- High reproducibility and long-term stability
- Reference accuracy: up to 0.3%
- Customized measuring ranges
 - Turn down up to 5:1
 - Sensor for measuring ranges up to 400 bar (6 000 psi)
- Housing and process isolating diaphragm made of 316L


















Table of contents

About this document	4	Reference accuracy	21
Document function	4	Thermal change of the zero output and the output span ...	21
Symbols	4	Long-term stability	21
Documentation	4	Switch-on time	21
Terms and abbreviations	6		
Turn down calculation	6	Mounting	22
		Installation conditions	22
Function and system design	7	Influence of orientation	22
Measuring principle - process pressure measurement	7	Mounting location	22
Measuring system	7	Mounting instructions for oxygen applications	23
Device features	8		
Product design	10	Environment	25
System integration	10	Ambient temperature range	25
		Storage temperature range	25
Input	11	Climate class	25
Measured variable	11	Degree of protection	25
Measuring range	11	Vibration resistance	25
		Electromagnetic compatibility	25
Output	15		
Output signal	15	Process	26
Signal range 4 to 20 mA	15	Process temperature range for devices with ceramic	
Load (for 4 to 20 mA devices)	15	process membrane	26
Load resistance (for 0 to 10 V devices)	15	Process temperature range for devices with metallic	
Signal on alarm 4 to 20 mA	15	process membrane	26
Dead time, time constant	15	Pressure specifications	27
Dynamic behavior	16		
		Mechanical construction	28
Power supply	17	Design, dimensions	28
Terminal assignment	17	Electrical connection	28
Supply voltage	17	Housing	29
Current consumption and alarm signal	17	Process connections with internal, ceramic process	
Power supply fault	18	membrane	31
Electrical connection	18	Process connections with internal, ceramic process	
Cable specification (analog)	18	membrane	32
Residual ripple	18	Process connections with internal, ceramic process	
Influence of power supply	18	membrane	33
Overvoltage protection	18	Process connections with internal, ceramic process	
		membrane	33
Performance characteristics of the ceramic		Process connections with internal, metal process	
process membrane	19	membrane	34
Reference conditions	19	Process connections with internal, metal process	
Uncertainty of measurement for small absolute pressure		membrane	35
ranges	19	Process connections with internal, metal process	
Influence of orientation	19	membrane	36
Resolution	19	Process connections with internal, metal process	
Reference accuracy	19	membrane	36
Thermal change of the zero output and the output span ...	19	Process connections with flush mount, metal process	
Long-term stability	19	membrane	37
Switch-on time	20	Materials in contact with process	38
		Materials not in contact with process	39
Performance characteristics of metallic process		Cleaning	40
membrane	21		
Reference conditions	21	Operability	41
Uncertainty of measurement for small absolute pressure		Plug-on display PHX20 (optional)	41
ranges	21		
Influence of orientation	21	Certificates and approvals	42
Resolution	21	CE mark	42

RoHS	42
RCM marking	42
EAC conformity	42
Approval	42
Safety Instructions (XA)	42
Marine approval	42
Pressure Equipment Directive 2014/68/EU (PED)	42
External standards and guidelines	43
CRN approval	44
Calibration unit	44
Calibration	44
Inspection certificates	44
Ordering information	44
Scope of delivery	45
Accessories	46
Weld-in adapter	46
Plug-on display PHX20	46
M12 plug-in jack	46
Supplemental documentation	47
Field of activities	47
Technical Information	47
Safety Instructions (XA)	47

About this document

Document function	The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.
Symbols	<p>Warning symbols</p> <p> DANGER</p> <p>This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.</p> <p> WARNING</p> <p>This symbol alerts you to a potentially dangerous situation. Failure to avoid this situation can result in serious or fatal injury.</p> <p> CAUTION</p> <p>This symbol alerts you to a potentially dangerous situation. Failure to avoid this situation can result in minor or medium injury.</p> <p> NOTICE</p> <p>This symbol alerts you to a potentially harmful situation. Failure to avoid this situation can result in damage to the product or something in its vicinity.</p> <p>Electrical symbols</p> <p> Protective earth (PE) Ground terminals, which must be grounded prior to establishing any other connections. The ground terminals are located on the inside and outside of the device.</p> <p> Ground connection Grounded clamp, which is grounded via a grounding system.</p> <p>Symbols for certain types of Information</p> <p> Permitted Procedures, processes or actions that are permitted.</p> <p> Forbidden Procedures, processes or actions that are forbidden.</p> <p> Tip Indicates additional information</p> <p> Reference to documentation</p> <p> 1, 2, 3 Series of steps</p> <p>Reference to page: </p> <p>Result of an individual step: </p> <p>Symbols in graphics</p> <p>A, B, C ... View</p> <p>1, 2, 3 ... Item numbers</p> <p> 1, 2, 3 Series of steps</p>
Documentation	<p>The following document types are available in the Downloads area of the Endress+Hauser website (www.endress.com/downloads):</p> <p> For an overview of the scope of the associated Technical Documentation, refer to the following:</p> <ul style="list-style-type: none"> ■ <i>Device Viewer</i> (www.endress.com/deviceviewer): Enter the serial number from the nameplate ■ <i>Endress+Hauser Operations app</i>: Enter serial number from nameplate or scan matrix code on nameplate.

Brief Operating Instructions (KA)

Guide that takes you quickly to the 1st measured value


The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning.

Operating Instructions (BA)

Reference document

These Operating Instructions contain all the information that is required in the various life cycle phases of the device: from product identification, incoming acceptance and storage, to installation, connection, operation and commissioning, through to troubleshooting, maintenance and disposal.

Terms and abbreviations




A0029505

- 1 OPL: The OPL (over pressure limit = sensor overload limit) for the measuring device depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to the measuring cell. Observe pressure-temperature dependency. The OPL may only be applied for a short period of time.
 - 2 MWP: The MWP (maximum working pressure) for the sensors depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to the measuring cell. Observe pressure-temperature dependency. The maximum working pressure may be applied at the device for an unlimited period. The MWP can be found on the nameplate.
 - 3 The maximum sensor measuring range corresponds to the span between the LRL and URL. This sensor measuring range is equivalent to the maximum calibratable/adjustable span.
 - 4 The calibrated/adjusted span corresponds to the span between the LRV and URV. Factory setting: 0 to URL. Other calibrated spans can be ordered as customized spans.
- p Pressure
 LRL Lower range limit
 URL Upper range limit
 LRV Lower range value
 URV Upper range value
 TD Turn down. Example - see the following section.

The turn down is preset at the factory and cannot be changed.

Turn down calculation



A0029545

- 1 Calibrated/adjusted span
- 2 Zero point-based span
- 3 Upper range limit

Example:

- Measuring cell: 10 bar (150 psi)
- Upper range limit (URL) = 10 bar (150 psi)
- Calibrated/adjusted span: 0 to 5 bar (0 to 75 psi)
- Lower range value (LRV) = 0 bar (0 psi)
- Upper range value (URV) = 5 bar (75 psi)

$$TD = \frac{URL}{|URV - LRV|}$$

In this example, the TD is 2:1. This span is based on the zero point.

Function and system design


Measuring principle - process pressure measurement

Devices with ceramic process membrane (Ceraphire®)

The ceramic sensor is an oil-free sensor, i.e. the process pressure acts directly on the robust ceramic process membrane and causes it to deflect. A pressure-dependent change in capacitance is measured at the electrodes of the ceramic substrate and the process membrane. The measuring range is determined by the thickness of the ceramic process membrane.

Advantages:

- Guaranteed overload resistance up to 40 times the nominal pressure
- Thanks to ultrapure 99.9 % ceramic (Ceraphire®, see also "www.endress.com/ceraphire")
 - Extremely high chemical durability
 - High mechanical durability
- Can be used in absolute vacuum
- Small measuring ranges



A0020465


- 1 Air pressure (relative pressure sensors)
- 2 Ceramic substrate
- 3 Electrodes
- 4 Ceramic process membrane

Devices with metallic process membrane

The process pressure deflects the metal process isolating diaphragm of the sensor and a fill fluid transfers the pressure to a Wheatstone bridge (semiconductor technology). The pressure-dependent change in the bridge output voltage is measured and evaluated.

Advantages:

- Can be used for high process pressures
- Fully welded sensor
- Slim, flush-mounted process connections available




A0016448

- 1 Silicon measuring element, substrate
- 2 Wheatstone bridge
- 3 Channel with fill fluid
- 4 Metallic process membrane

Measuring system

A complete measuring system comprises:



A0021926

- 1 PLC (programmable logic controller)
 2 E.g. RN221N/RMA42 (if required)
 3 Pressure transducer

Device features

Field of application

- PMC11, PMP11: gauge pressure
- PMC21, PMP21: gauge pressure and absolute pressure

Process connections

PMC11:

- Thread ISO 228
- Thread ASME
- DIN 13

PMP11:

- Thread ISO 228, also flush mount
- Thread ASME
- DIN 13

PMC21:

- Thread ISO 228
- DIN 13 thread
- Thread ASME
- JIS thread

PMP21:

- Thread ISO 228, also flush mount
- DIN 13 thread
- Thread ASME
- JIS thread

Measuring ranges

- PMC11: from -400 to +400 mbar (-6 to +6 psi) to -1 to +40 bar (-15 to +600 psi).
- PMP11: from -400 to +400 mbar (-6 to +6 psi) to -1 to +40 bar (-15 to +600 psi).
- PMC21: from -100 to +100 mbar (-1.5 to +1.5 psi) to -1 to +40 bar (-15 to +600 psi).
- PMP21: from -400 to +400 mbar (-6 to +6 psi) to -1 to +400 bar (-15 to +6 000 psi).

OPL (depends on the measuring range)

- PMC11, PMC21: max. 0 to +60 bar (0 to +900 psi)
- PMP11: max. 0 to +160 bar (0 to +2 400 psi)
- PMP21: max. 0 to +600 bar (0 to +9 000 psi)

MWP

- PMC11, PMC21: max. 0 to +40 bar (0 to +600 psi)
- PMP11: max. 0 to +100 bar (0 to +1 500 psi)
- PMP21: max. 0 to +400 bar (0 to +6 000 psi)

Process temperature range (temperature at process connection)

- PMC11, PMP11: -25 to +85 °C (-13 to +185 °F)
- PMC21: -25 to +100 °C (-13 to +212 °F)
- PMP21: -40 to +100 °C (-40 to +212 °F)

Ambient temperature range

- PMC11, PMP11: -40 to +70 °C (-40 to +158 °F)
- PMC21:
 - -40 to +85 °C (-40 to +185 °F)
 - Devices for hazardous areas: -40 to +70 °C (-40 to +158 °F)
- PMP21:
 - -40 to +85 °C (-40 to +185 °F)

Reference accuracy

PMC11, PMP11:

Up to 0.5 %, TD 5:1, see reference accuracy section for details.

PMC21, PMP21:

Up to 0.3 %, TD 5:1, see reference accuracy section for details.

Supply voltage

PMC11, PMP11:

- 4 to 20 mA output: 10 to 30 V_{DC}
- 0 to 10 V output: 12 to 30 V_{DC}

PMC21, PMP21:

10 to 30 V_{DC}

Output

- 4 to 20 mA
- 0 to 10 V

PMC21, PMP21:

4 to 20 mA

Material

PMC11; PMC21:

- Housing made of 316L (1.4404)
- Process connections made of 316L
- Process membrane made of Al₂O₃ aluminum-oxide ceramic, (Ceraphire®), ultrapure 99.9 %

PMP11, PMP21:

- Housing made of 316L (1.4404)
- Process connections made of 316L (1.4404)
- Process membrane made of 316L (1.4435)

Options

PMC11, PMP11:


- Calibration certificate
- Cleaned of oil and grease

PMC21:

- Hazardous area approvals
- Marine approvals
- Min. setting Alarm current
- 3.1 Material certificates
- Calibration certificate
- Cleaned of oil and grease
- Cleaned for O₂ applications

PMP21:

- Hazardous area approvals
- Marine approvals
- Min. setting Alarm current
- 3.1 Material certificates
- Calibration certificate
- Cleaned of oil and grease

Overview	Item	Description
	A	Valve plug
	B	Cable
	C- 1	M12 plug Housing cap made of plastic
	C- 2	M12 plug For Ex ec and IP69: metal housing cap
	D E	Housing Process connection (sample illustration)

System integration

The device can be given a tag name (max. 32 alphanumeric characters).

Name	Option ¹⁾
Measuring point (TAG); see additional specifications	Z1

1) Product Configurator, order code for "Marking"

Input

Measured variable

Measured process variable

- PMC11, PMP11: gauge pressure
- PMC21, PMP21: gauge pressure and absolute pressure

Calculated process variable

Pressure

Measuring range

Ceramic process membrane

Devices for gauge pressure measurement

Sensor	Device	Maximum sensor measuring range		Smallest calibratable span ¹⁾	MWP	OPL	Factory settings ²⁾	Option ³⁾
		lower (LRL)	upper (URL)					
		[bar (psi)]	[bar (psi)]					
100 mbar (1.5 psi) ⁴⁾	PMC21	-0.1 to -1.5	+0.1 (+1.5)	0.02 (0.3)	2.7 (40.5)	4 (60)	0 to 100 mbar (0 to 1.5 psi)	1C
250 mbar (4 psi) ⁵⁾	PMC21	-0.25 (-4)	+0.25 (+4)	0.05 (1)	3.3 (49.5)	5 (75)	0 to 250 mbar (0 to 4 psi)	1E
400 mbar (6 psi) ⁶⁾	PMC11 PMC21	-0.4 (-6)	+0.4 (+6)	0.08 (1.2)	5.3 (79.5)	8 (120)	0 to 400 mbar (0 to 6 psi)	1F
1 bar (15 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+1 (+15)	0.2 (3)	6.7 (100.5)	10 (150)	0 to 1 bar (0 to 15 psi)	1H
2 bar (30 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+2 (+30)	0.4 (6)	12 (180)	18 (270)	0 to 2 bar (0 to 30 psi)	1K
4 bar (60 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+4 (+60)	0.8 (12)	16.7 (250.5)	25 (375)	0 to 4 bar (0 to 60 psi)	1M
6 bar (90 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+6 (+90)	2.4 (36)	26.7 (400.5)	40 (600)	0 to 6 bar (0 to 90 psi)	1N
10 bar (150 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+10 (+150)	2 (30)	26.7 (400.5)	40 (600)	0 to 10 bar (0 to 150 psi)	1P
16 bar (240 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+16 (+240)	6.4 (96)	40 (600)	60 (900)	0 to 16 bar (0 to 240 psi)	1Q
25 bar (375 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+25 (+375)	10 (150)	40 (600)	60 (900)	0 to 25 bar (0 to 375 psi)	1R
40 bar (600 psi) ⁶⁾	PMC11 PMC21	-1 (-15)	+40 (+600)	8 (120)	40 (600)	60 (900)	0 to 40 bar (0 to 600 psi)	1S

1) Highest turn down that can be set at the factory: 5:1. The turn down is preset and cannot be changed.

2) Other measuring ranges (e.g. -1 to +5 bar (-15 to 75 psi)) can be ordered with customer-specific settings (see the Product Configurator, order code for "Calibration; Unit" option "J"). It is possible to invert the output signal (LRV = 20 mA; URV = 4 mA). Prerequisite: URV < LRV

3) Product Configurator, order code for "Sensor range"

4) Vacuum resistance: 0.7 bar (10.5 psi) abs.

5) Vacuum resistance: 0.5 bar (7.5 psi) abs.

6) Vacuum resistance: 0 bar (0 psi) abs.

Devices for absolute pressure measurement

Sensor	Device	Maximum sensor measuring range		Smallest calibratable span ¹⁾	MWP	OPL	Factory settings ²⁾	Option ³⁾
		lower (LRL)	upper (URL)					
		[bar (psi)]	[bar (psi)]					
100 mbar (1.5 psi)	PMC21	0	+0.1 (+1.5)	0.1 (1.5)	2.7 (40.5)	4 (60)	0 to 100 mbar (0 to 1.5 psi)	2C
250 mbar (4 psi)	PMC21	0	+0.25 (+4)	0.25 (4)	3.3 (49.5)	5 (75)	0 to 250 mbar (0 to 4 psi)	2E
400 mbar (6 psi)	PMC21	0	+0.4 (+6)	0.4 (6)	5.3 (79.5)	8 (120)	0 to 400 mbar (0 to 6 psi)	2F
1 bar (15 psi)	PMC21	0	+1 (+15)	0.4 (6)	6.7 (100.5)	10 (150)	0 to 1 bar (0 to 15 psi)	2H
2 bar (30 psi)	PMC21	0	+2 (+30)	0.4 (6)	12 (180)	18 (270)	0 to 2 bar (0 to 30 psi)	2K
4 bar (60 psi)	PMC21	0	+4 (+60)	0.8 (12)	16.7 (250.5)	25 (375)	0 to 4 bar (0 to 60 psi)	2M
10 bar (150 psi)	PMC21	0	+10 (+150)	2 (30)	26.7 (400.5)	40 (600)	0 to 10 bar (0 to 150 psi)	2P
40 bar (600 psi)	PMC21	0	+40 (+600)	8 (120)	40 (600)	60 (900)	0 to 40 bar (0 to 600 psi)	2S

1) Highest turn down that can be set at the factory: 5:1. The turn down is preset and cannot be changed.

2) Other measuring ranges (e.g. -1 to +5 bar (-15 to 75 psi)) can be ordered with customer-specific settings (see the Product Configurator, order code for "Calibration; Unit" option "J"). It is possible to invert the output signal (LRV = 20 mA; URV = 4 mA). Prerequisite: URV < LRV

3) Product Configurator, order code for "Sensor range"

Maximum turn down which can be ordered for absolute pressure and gauge pressure sensors

Devices for gauge pressure measurement

- 6 bar (90 psi), 16 bar (240 psi), 25 bar (375 psi): TD 1:1 to TD 2.5:1
- All other measuring ranges: TD 1:1 to TD 5:1

Devices for absolute pressure measurement

- 100 mbar (1.5 psi), 250 mbar (4 psi), 400 mbar (6 psi): TD 1:1
- 1 bar (15 psi): TD 1:1 to TD 2.5:1
- All other measuring ranges: TD 1:1 to TD 5:1

Metallic process membrane*Devices with gauge pressure measurement*

Sensor	Device	Maximum sensor measuring range		Smallest calibratable span ¹⁾	MWP	OPL	Factory settings ²⁾	Option ³⁾
		lower (LRL)	upper (URL)					
		[bar (psi)]	[bar (psi)]					
400 mbar (6 psi) ⁴⁾	PMP11 PMP21	-0.4 (-6)	+0.4 (+6)	0.4 (6)	1 (15)	1.6 (24)	0 to 400 mbar (0 to 6 psi)	1F
1 bar (15 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+1 (+15)	0.4 (6)	2.7 (40.5)	4 (60)	0 to 1 bar (0 to 15 psi)	1H
2 bar (30 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+2 (+30)	0.4 (6)	6.7 (100.5)	10 (150)	0 to 2 bar (0 to 30 psi)	1K
4 bar (60 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+4 (+60)	0.8 (12)	10.7 (160.5)	16 (240)	0 to 4 bar (0 to 60 psi)	1M
6 bar (90 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+6 (+90)	2.4 (36)	16 (240)	24 (360)	0 to 6 bar (0 to 90 psi)	1N
10 bar (150 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+10 (+150)	2 (30)	25 (375)	40 (600)	0 to 10 bar (0 to 150 psi)	1P
16 bar (240 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+16 (+240)	5 (75)	25 (375)	64 (960)	0 to 16 bar (0 to 240 psi)	1Q
25 bar (375 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+25 (+375)	5 (75)	25 (375)	100 (1500)	0 to 25 bar (0 to 375 psi)	1R
40 bar (600 psi) ⁴⁾	PMP11 PMP21	-1 (-15)	+40 (+600)	8 (120)	100 (1500)	160 (2400)	0 to 40 bar (0 to 600 psi)	1S
100 bar (1 500 psi) ⁴⁾	PMP21	-1 (-15)	+100 (+1500)	20 (300)	100 (1500)	160 (2400)	0 to 100 bar (0 to 1 500 psi)	1U
400 bar (6 000 psi) ⁴⁾	PMP21	-1 (-15)	+400 (+6000)	80 (1200)	400 (6000)	600 (9000)	0 to 400 bar (0 to 6 000 psi)	1W

- 1) Highest turn down that can be set at the factory: 5:1. The turn down is preset and cannot be changed.
- 2) Other measuring ranges (e.g. -1 to +5 bar (-15 to 75 psi)) can be ordered with customer-specific settings (see the Product Configurator, order code for "Calibration; Unit" option "J"). It is possible to invert the output signal (LRV = 20 mA; URV = 4 mA). Prerequisite: URV < LRV
- 3) Product Configurator, order code for "Sensor range"
- 4) Vacuum resistance: 0.01 bar (0.145 psi) abs.

Devices with absolute pressure measurement

Sensor	Device	Maximum sensor measuring range		Smallest calibratable span ¹⁾	MWP	OPL	Factory settings ²⁾	Option ³⁾
		lower (LRL)	upper (URL)					
		[bar (psi)]	[bar (psi)]					
400 mbar (6 psi)	PMP21	0 (0)	0.4 (+6)	0.4 (6)	1 (15)	1.6 (24)	0 to 400 mbar (0 to 6 psi)	2F
1 bar (15 psi)	PMP21	0 (0)	1 (+15)	0.4 (6)	2.7 (40.5)	4 (60)	0 to 1 bar (0 to 15 psi)	2H
2 bar (30 psi)	PMP21	0 (0)	2 (+30)	0.4 (6)	6.7 (100.5)	10 (150)	0 to 2 bar (0 to 30 psi)	2K
4 bar (60 psi)	PMP21	0 (0)	4 (+60)	0.8 (12)	10.7 (160.5)	16 (240)	0 to 4 bar (0 to 60 psi)	2M
10 bar (150 psi)	PMP21	0 (0)	10 (+150)	2 (30)	25 (375)	40 (600)	0 to 10 bar (0 to 150 psi)	2P
40 bar (600 psi)	PMP21	0 (0)	+40 (+600)	8 (120)	100 (1500)	160 (2400)	0 to 40 bar (0 to 600 psi)	2S
100 bar (1 500 psi)	PMP21	0 (0)	+100 (+1500)	20 (300)	100 (1500)	160 (2400)	0 to 100 bar (0 to 1 500 psi)	2U
400 bar (6 000 psi)	PMP21	0 (0)	+400 (+6000)	80 (1200)	400 (6000)	600 (9000)	0 to 400 bar (0 to 6 000 psi)	2W

- 1) Highest turn down that can be set at the factory: 5:1. The turn down is preset and cannot be changed.
- 2) Other measuring ranges (e.g. -1 to +5 bar (-15 to 75 psi)) can be ordered with customer-specific settings (see the Product Configurator, order code for "Calibration; Unit" option "J"). It is possible to invert the output signal (LRV = 20 mA; URV = 4 mA). Prerequisite: URV < LRV
- 3) Product Configurator, order code for "Sensor range"

Maximum turn down which can be ordered for absolute pressure and gauge pressure sensors

Device	Range	400 mbar (6 psi)	1 bar (15 psi) 6 bar (90 psi) 16 bar (240 psi)	2 bar (30 psi) 4 bar (60 psi) 10 bar (150 psi) 25 to 400 bar (375 to 6 000 psi)
PMP11	0.5%	TD 1:1	TD 1:1 to TD 2.5:1	TD 1:1 to TD 5:1
PMP21	0.3%	TD 1:1	TD 1:1 to TD 2.5:1	TD 1:1 to TD 5:1


Output

Output signal	Description	Option ¹⁾
	4 to 20 mA (2-wire)	1
	0 to 10 V output (3-wire)	2

1) Product Configurator, order code for "Output"

Signal range 4 to 20 mA 3.8 to 20.5 mA

Load (for 4 to 20 mA devices) In order to guarantee sufficient terminal voltage in two-wire devices, a maximum load resistance R_L (including line resistance) must not be exceeded depending on the supply voltage U_B of the supply unit.



A0029452

- 1 Power supply 10 to 30 V DC
- 2 R_{Lmax} maximum load resistance
- U_B Supply voltage

Load resistance (for 0 to 10 V devices) The load resistance must be ≥ 5 [kΩ].


Signal on alarm 4 to 20 mA The response of the output to error is regulated in accordance with NAMUR NE 43.
Factory setting MAX alarm: >21 mA

Alarm current

Name	Option
Min. alarm current set	IA ¹⁾

1) Product Configurator, order code for "Service"

Dead time, time constant Presentation of the dead time and the time constant:



A0019786

Dynamic behavior

Dead time (t_1) [ms]	Time constant (T63), t_2 [ms]	Time constant (T90), t_3 [ms]
6 ms	10 ms	15 ms

Power supply

⚠ WARNING

Reduced electrical safety due to incorrect connection!

- ▶ A suitable circuit breaker must be provided for the device in accordance with IEC/EN 61010.
- ▶ When using the measuring instrument in hazardous areas, installation must also comply with the applicable national standards and regulations and the Safety Instructions or Installation or Control Drawings.
- ▶ All explosion protection data are provided in separate Ex documentation, which is available on request. The Ex documentation is supplied as standard with all devices approved for use in explosion hazardous areas.
- ▶ Protective circuits against reverse polarity, HF influences and overvoltage peaks are installed.
- ▶ **Non-hazardous area:** To meet device safety specifications according to the IEC/EN61010 standard, the installation must ensure that the maximum current is limited to 630 mA.
- ▶ **Hazardous area:** The maximum current is restricted to $I_i = 100 \text{ mA}$ by the transmitter power supply unit when the measuring instrument is used in an intrinsically safe circuit (Ex ia).




Terminal assignment

NOTICE



Damage to analog input of PLC resulting from incorrect connection

- ▶ Do not connect the active PNP switch output of the device to the 4 to 20 mA input of a PLC.

4 to 20 mA output

Device	M12 plug	Valve plug	Cables
PMC11 PMP11 PMC21 PMP21			
			1 brown = L+ 2 blue = L- 3 green/yellow = ground connection (a) reference air hose

0 to 10 V output (not for IO-Link)

Device	M12 plug	Valve plug	Cables
PMC11 PMP11			-

Supply voltage

Electronic version	Supply voltage
4 to 20 mA output	10 to 30 V DC
0 to 10 V output	12 to 30 V DC

Current consumption and alarm signal

Electronic version	Current consumption	Alarm signal ¹⁾
4 to 20 mA output	≤ 26 mA	> 21 mA
0 to 10 V output	< 12 mA	11 V

1) For MAX alarm (factory setting)

Power supply fault

- Behavior in the event of overvoltage (>30 V):
The device works continuously up to 34 V DC without damage. If the supply voltage is exceeded, the specified characteristics are no longer guaranteed.
- Behavior in the event of undervoltage:
If the supply voltage falls below the minimum value, the device switches off in a defined manner.

Electrical connection**Degree of protection**

Communication version	Device	Connector	Degree of protection	Option ¹⁾
Analog	PMC21 PMP21	Cable 5 m (16 ft)	IP66/68 ²⁾ NEMA Type 4X/6P enclosure	A
	PMC21 PMP21	Cable 10 m (33 ft)	IP66/68 ²⁾ NEMA Type 4X/6P enclosure	B
	PMC21 PMP21	Cable 25 m (82 ft)	IP66/68 ²⁾ NEMA Type 4X/6P enclosure	C
	PMC11 PMP11	M12 plug	IP65 NEMA Type 4X enclosure	L
	PMC11 PMP11 PMC21 PMP21	Valve plug ISO4400 M16	IP65 NEMA Type 4X enclosure	U
	PMC11 PMP11 PMC21 PMP21	Valve plug ISO4400 NPT ½	IP65 NEMA Type 4X enclosure	V
Analog, IO-Link	PMC21 PMP21	M12 plug	IP65/67 NEMA Type 4X enclosure	M

1) Product Configurator, order code for "Electrical connection"

2) IP 68 (1.83m H2O for 24 h)

Cable specification (analog)

For valve plug: < 1.5 mm² (16 AWG) and Ø 4.5 to 10 mm (0.18 to 0.39 in)

Residual ripple

The device operates within the reference accuracy up to ±5 % of the residual ripple of the supply voltage, within the permitted voltage range.



Influence of power supply

≤0.005 % of URV/1 V

Overvoltage protection

The device does not contain any special elements to protect against overvoltage ("wire to ground"). Nevertheless the requirements of the applicable EMC standard EN 61000-4-5 (testing voltage 1kV EMC wire/ground) are met.

Performance characteristics of the ceramic process membrane

Reference conditions	<ul style="list-style-type: none">■ As per IEC 60770■ Ambient temperature T_A = constant, in the range of: +21 to +33 °C (+70 to +91 °F)■ Humidity φ = constant, in the range of 5 to 80 % rH■ Atmospheric pressure p_A = constant, in the range of: 860 to 1 060 mbar (12.47 to 15.37 psi)■ Position of the measuring cell = constant, in the range of: horizontal ±1° (see also "Influence of orientation" section)■ Zero based span■ Material of process membrane: Al₂O₃ (aluminum-oxide ceramic, Ceraphire®)■ Supply voltage: 24 V DC ±3 V DC■ Load: 320 Ω (at 4 to 20 mA output)																									
Uncertainty of measurement for small absolute pressure ranges	<p>The smallest extended uncertainty of measurement that can be delivered by our standards is</p> <ul style="list-style-type: none">■ in the range of 1 to 30 mbar (0.0145 to 0.435 psi): 0.4 % of reading■ in the range of < 1 mbar (0.0145 psi): 1 % of reading.																									
Influence of orientation	→  22																									
Resolution	Current output: min. 1.6 µA																									
Reference accuracy	<p>The reference accuracy includes the non-linearity [DIN EN 61298-2 3.11] including the pressure hysteresis [DIN EN 61298-23.13] and non-repeatability [DIN EN 61298-2 3.11] in accordance with the limit point method as per [DIN EN 60770].</p> <table><tr><th rowspan="2">Device</th><th colspan="3">% of the calibrated span to the maximum turn down</th></tr><tr><th>Reference accuracy</th><th>Non-linearity ¹⁾</th><th>Non-repeatability</th></tr><tr><td>PMC11 ²⁾</td><td>±0.5</td><td>±0.1</td><td>±0.1</td></tr><tr><td>PMC21</td><td>±0.3</td><td>±0.1</td><td>±0.1</td></tr></table> <p>1) The non-linearity for the 40 bar (600 psi) sensor can be up to ± 0.15% of the calibrated span up to the maximum turn down.</p> <p>2) For devices with 0 to 10 V output, a non-linearity of up to max. 0.3 V can occur for signal values below 0.03 V.</p> <p>Overview of the turn down ranges →  12</p> <table><tr><th>Measuring ranges</th><th>Turn down</th><th>Device</th><th>% of the URL</th></tr><tr><td rowspan="2">100 mbar (1.5 psi) to 40 bar (600 psi)</td><td rowspan="2">1:1 to TD 5:1</td><td>PMC11</td><td>±0.5</td></tr><tr><td>PMC21</td><td>±0.3 ¹⁾</td></tr></table> <p>1) For the 100 mbar (1.5 psi) and 250 mbar (4 psi) measuring ranges, the following applies: In the event of heat effects on the initial reference conditions, an additional deviation of max. 0.3 mbar (4.5 psi) from the zero point or the output span is possible.</p>	Device	% of the calibrated span to the maximum turn down			Reference accuracy	Non-linearity ¹⁾	Non-repeatability	PMC11 ²⁾	±0.5	±0.1	±0.1	PMC21	±0.3	±0.1	±0.1	Measuring ranges	Turn down	Device	% of the URL	100 mbar (1.5 psi) to 40 bar (600 psi)	1:1 to TD 5:1	PMC11	±0.5	PMC21	±0.3 ¹⁾
Device	% of the calibrated span to the maximum turn down																									
	Reference accuracy	Non-linearity ¹⁾	Non-repeatability																							
PMC11 ²⁾	±0.5	±0.1	±0.1																							
PMC21	±0.3	±0.1	±0.1																							
Measuring ranges	Turn down	Device	% of the URL																							
100 mbar (1.5 psi) to 40 bar (600 psi)	1:1 to TD 5:1	PMC11	±0.5																							
		PMC21	±0.3 ¹⁾																							
Thermal change of the zero output and the output span	<table><tr><th rowspan="2">Measuring cell</th><th>-20 to +85 °C (-4 to +185 °F)</th><th>-40 to -20 °C (-40 to -4 °F) +85 to +100 °C (+185 to +212 °F)</th></tr><tr><th colspan="2">% of the URL for TD 1:1</th></tr><tr><td><1 bar (15 psi)</td><td><1</td><td><1.2</td></tr><tr><td>≥1 bar (15 psi)</td><td><0.8</td><td><1</td></tr></table>	Measuring cell	-20 to +85 °C (-4 to +185 °F)	-40 to -20 °C (-40 to -4 °F) +85 to +100 °C (+185 to +212 °F)	% of the URL for TD 1:1		<1 bar (15 psi)	<1	<1.2	≥1 bar (15 psi)	<0.8	<1														
Measuring cell	-20 to +85 °C (-4 to +185 °F)		-40 to -20 °C (-40 to -4 °F) +85 to +100 °C (+185 to +212 °F)																							
	% of the URL for TD 1:1																									
<1 bar (15 psi)	<1	<1.2																								
≥1 bar (15 psi)	<0.8	<1																								
Long-term stability	<table><tr><th>1 year</th><th>5 years</th><th>8 years</th></tr><tr><th colspan="3">% of the URL</th></tr><tr><td>±0.2</td><td>±0.4</td><td>±0.45</td></tr></table>	1 year	5 years	8 years	% of the URL			±0.2	±0.4	±0.45																
1 year	5 years	8 years																								
% of the URL																										
±0.2	±0.4	±0.45																								

Switch-on time ≤ 2 s

For small measuring ranges, pay attention to the thermal compensation effects.

Performance characteristics of metallic process membrane

Reference conditions	<ul style="list-style-type: none">■ As per IEC 60770■ Ambient temperature T_A = constant, in the range of: +21 to +33 °C (+70 to +91 °F)■ Humidity φ = constant, in the range of: 5 to 80 % rH■ Atmospheric pressure p_A = constant, in the range of: 860 to 1060 mbar (12.47 to 15.37 psi)■ Position of the measuring cell = constant, in the range of: horizontal ±1° (see also "Influence of orientation" section)■ Zero based span■ Process membrane material: AISI 316L (1.4435)■ Filling oil: synthetic oil polyalphaolefin FDA 21 CFR 178.3620, NSF H1■ Supply voltage: 24 V DC ±3 V DC■ Load: 320 Ω (at 4 to 20 mA output)															
Uncertainty of measurement for small absolute pressure ranges	<p>The smallest extended uncertainty of measurement that can be delivered by our standards is</p> <ul style="list-style-type: none">■ in the range of 1 to 30 mbar (0.0145 to 0.435 psi): 0.4 % of reading■ in the range of < 1 mbar (0.0145 psi): 1 % of reading.															
Influence of orientation	→ 📄 22															
Resolution	Current output: min. 1.6 µA															
Reference accuracy	<p>The reference accuracy includes the non-linearity [DIN EN 61298-2 3.11] including the pressure hysteresis [DIN EN 61298-23.13] and non-repeatability [DIN EN 61298-2 3.11] in accordance with the limit point method as per [DIN EN 60770].</p> <table><tr><th rowspan="2">Device</th><th colspan="3">% of the calibrated span to the maximum turn down</th></tr><tr><th>Reference accuracy</th><th>Non-linearity</th><th>Non-repeatability</th></tr><tr><td>PMP11 ¹⁾</td><td>±0.5</td><td>±0.1</td><td>±0.1</td></tr><tr><td>PMP21</td><td>±0.3</td><td>±0.1</td><td>±0.1</td></tr></table> <p>1) For devices with 0 to 10 V output, a non-linearity of up to 0.3 V max. can occur for signal values below 0.015 V.</p> <p>Overview of the turn down ranges → 📄 14</p>	Device	% of the calibrated span to the maximum turn down			Reference accuracy	Non-linearity	Non-repeatability	PMP11 ¹⁾	±0.5	±0.1	±0.1	PMP21	±0.3	±0.1	±0.1
Device	% of the calibrated span to the maximum turn down															
	Reference accuracy	Non-linearity	Non-repeatability													
PMP11 ¹⁾	±0.5	±0.1	±0.1													
PMP21	±0.3	±0.1	±0.1													
Thermal change of the zero output and the output span	<table><tr><th rowspan="2">Measuring cell</th><th>-20 to +85 °C (-4 to +185 °F)</th><th>-40 to -20 °C (-40 to -4 °F) +85 to +100 °C (+185 to +212 °F)</th></tr><tr><th colspan="2">% of the calibrated span for TD 1:1</th></tr><tr><td><1 bar (15 psi)</td><td><1</td><td><1.2</td></tr><tr><td>≥1 bar (15 psi)</td><td><0.8</td><td><1</td></tr></table>	Measuring cell	-20 to +85 °C (-4 to +185 °F)	-40 to -20 °C (-40 to -4 °F) +85 to +100 °C (+185 to +212 °F)	% of the calibrated span for TD 1:1		<1 bar (15 psi)	<1	<1.2	≥1 bar (15 psi)	<0.8	<1				
Measuring cell	-20 to +85 °C (-4 to +185 °F)		-40 to -20 °C (-40 to -4 °F) +85 to +100 °C (+185 to +212 °F)													
	% of the calibrated span for TD 1:1															
<1 bar (15 psi)	<1	<1.2														
≥1 bar (15 psi)	<0.8	<1														
Long-term stability	<p>Analog</p> <table><tr><th>1 year</th><th>5 years</th><th>8 years</th></tr><tr><th colspan="3">% of the URL</th></tr><tr><td>±0.2</td><td>±0.4</td><td>±0.45</td></tr></table>	1 year	5 years	8 years	% of the URL			±0.2	±0.4	±0.45						
1 year	5 years	8 years														
% of the URL																
±0.2	±0.4	±0.45														
Switch-on time	≤2 s															


Mounting

Installation conditions

- Moisture must not penetrate the housing when mounting the device, establishing the electrical connection and during operation.
- Point the cable and connector downwards where possible to prevent moisture from entering (e.g. rain or condensation water).

Influence of orientation

Any orientation is possible. However, the orientation may cause a zero point shift, i.e. the measured value does not show zero when the vessel is empty or partially full.



A0024708

PMP11, PMP21

Process membrane axis is horizontal (A)	Process membrane pointing upwards (B)	Process membrane pointing downwards (C)
Calibration position, no effect	Up to +4 mbar (+0.058 psi)	Up to -4 mbar (-0.058 psi)

PMC11, PMC21


Type	Process membrane axis is horizontal (A)	Process membrane pointing upwards (B)	Process membrane pointing downwards (C)
< 1 bar (15 psi)	Calibration position, no effect	Up to +0.3 mbar (+0.0044 psi)	Up to -0.3 mbar (-0.0044 psi)
≥ 1 bar (15 psi)	Calibration position, no effect	Up to +3 mbar (+0.0435 psi)	Up to -3 mbar (-0.0435 psi)

Mounting location

Pressure measurement

Pressure measurement in gases

Mount the device with shutoff device above the tapping point so that any condensate can flow into the process.



A0021904

- 1 Device
2 Shutoff device


Pressure measurement in vapors

For pressure measurement in vapors, use a siphon. The siphon reduces the temperature to almost ambient temperature. Mount the device with a shutoff device at the same height as the tapping point.

Advantage:

only minor/negligible heat effects on the device.

Note the max. permitted ambient temperature of the transmitter!




A0024395

- 1 Device
- 2 Shutoff device
- 3 Siphon

Pressure measurement in liquids

Mount the device with a shutoff device at the same height as the tapping point.




A0024399

- 1 Device
- 2 Shutoff device

Level measurement

- Always install the device below the lowest measuring point.
- Do not install the device at the following positions:
 - in the filling curtain
 - in the tank outlet
 - in the suction area of a pump
 - at a point in the tank which could be affected by pressure pulses from the agitator.



A0024405

Mounting instructions for oxygen applications

Oxygen and other gases can react explosively to oils, grease and plastics, such that, among other things, the following precautions must be taken:

- All components of the system, such as measuring devices, must be cleaned in accordance with the BAM requirements.
- Depending on the materials used, a certain maximum temperature and a maximum pressure must not be exceeded for oxygen applications.
- The following table lists devices (devices only, not accessories or enclosed accessories), which are suitable for gaseous oxygen applications.

PMC21

p_{max} for oxygen applications	T_{max} for oxygen applications	Option ¹⁾
40 bar (600 psi)	-10 to +60 °C (+14 to +140 °F)	HB

1) Product Configurator, order code for "Service"

Environment

Ambient temperature range	Ambient temperature range ¹⁾ <ul style="list-style-type: none"> ■ -40 to +70 °C (-40 to +158 °F) ■ Devices for hazardous areas: -40 to +70 °C (-40 to +158 °F) ■ Analog: -40 to +85 °C (-40 to +185 °F) ■ IO-Link: -40 to +70 °C (-40 to +158 °F)
Storage temperature range	-40 to +85 °C (-40 to +185 °F)

Climate class	Climate class	Note
	Class 3K5	Air temperature: -5 to +45 °C (+23 to +113 °F), relative humidity: 4 to 95 % satisfied according to IEC 721-3-3 (condensation not possible)

Degree of protection	Communication version	Device	Connector	Degree of protection	Option ¹⁾
	Analog	PMC21 PMP21	Cable 5 m (16 ft)	IP66/68 ²⁾ NEMA Type 4X/6P enclosure	A
		PMC21 PMP21	Cable 10 m (33 ft)	IP66/68 ²⁾ NEMA Type 4X/6P enclosure	B
		PMC21 PMP21	Cable 25 m (82 ft)	IP66/68 ²⁾ NEMA Type 4X/6P enclosure	C
		PMC11 PMP11	M12 plug	IP65 NEMA Type 4X enclosure	L
		PMC11 PMP11 PMC21 PMP21	Valve plug ISO4400 M16	IP65 NEMA Type 4X enclosure	U
		PMC11 PMP11 PMC21 PMP21	Valve plug ISO4400 NPT ½	IP65 NEMA Type 4X enclosure	V
	Analog, IO-Link	PMC21 PMP21	M12 plug	IP65/67 NEMA Type 4X enclosure	M

1) Product Configurator, order code for "Electrical connection"

2) IP 68 (1.83m H₂O for 24 h)

Vibration resistance	Test standard	Vibration resistance
	IEC 60068-2-64:2008	Guaranteed for 5 to 2000Hz: 0.05g ² /Hz

Electromagnetic compatibility	<ul style="list-style-type: none"> ■ Interference emission as per EN 61326-1 equipment B ■ Interference immunity as per EN 61326-1 (industrial environment) ■ NAMUR recommendation EMC (NE 21) ■ Maximum deviation: 1.5% with TD 1:1
--------------------------------------	--

For more details please refer to the Declaration of Conformity.

1) Exception: the following cable is designed for an ambient temperature range of -25 to +70 °C (-13 to +158 °F): Product Configurator, order code for "Accessory enclosed" option "RZ".

Process

Process temperature range for devices with ceramic process membrane

PMC11

–25 to +85 °C (–13 to +185 °F)

PMC21

- –25 to +100 °C (–13 to +212 °F)
- with oxygen applications:
–10 to +60 °C (+14 to +140 °F)
- For saturated steam applications, use a device with a metallic process membrane, or provide a siphon for temperature isolation when installing.
- Observe the process temperature range of the seal. See also the following table.

Seal	Notes	Process temperature range	Option
FKM	-	–20 to +100 °C (–4 to +212 °F)	A ¹⁾
FKM	Cleaned for O ₂ application	–10 to +60 °C (+14 to +140 °F)	A ¹⁾ and HB ²⁾
EPDM 70	-	–25 to +100 °C (–13 to +212 °F)	J ¹⁾

1) Product Configurator, order code for "Seal"

2) Product Configurator, order code for "Service"

Applications with jumps in temperature

Frequent extreme changes in temperatures can temporarily cause measuring errors. Temperature compensation occurs after a few minutes. Internal temperature compensation occurs more quickly the smaller the change in temperature and the longer the time interval involved.

For further information please contact your local Endress+Hauser Sales Center.

Process temperature range for devices with metallic process membrane

PMP11

–25 to +85 °C (–13 to +185 °F)

PMP21

–40 to +100 °C (–40 to +212 °F)

Applications with jumps in temperature

Frequent extreme changes in temperatures can temporarily cause measuring errors. Internal temperature compensation occurs more quickly the smaller the change in temperature and the longer the time interval involved.

For further information please contact your local Endress+Hauser Sales Center.

Pressure specifications

WARNING

The maximum pressure for the measuring device depends on the lowest-rated element with regard to pressure.

- ▶ For pressure specifications, see the "Measuring range" section and the "Mechanical construction" section.
- ▶ The Pressure Equipment Directive (2014/68/EU) uses the abbreviation "PS". The abbreviation "PS" corresponds to the MWP (maximum working pressure) of the measuring device.
- ▶ MWP (maximum working pressure): The MWP (maximum working pressure) is specified on the nameplate. This value is based on a reference temperature of +20 °C (+68 °F) and may be applied to the device for an unlimited period of time. Observe the temperature dependency of the MWP.
- ▶ OPL (over pressure limit): The test pressure corresponds to the over pressure limit of the sensor and may only be applied temporarily to ensure that the measurement is within the specifications and no permanent damage develops. In the case of sensor range and process connections where the over pressure limit (OPL) of the process connection is smaller than the nominal value of the sensor, the device is set at the factory, at the very maximum, to the OPL value of the process connection. If you want to use the entire sensor range, select a process connection with a higher OPL value.
- ▶ Oxygen applications: In oxygen applications, the values for p_{\max} and T_{\max} for oxygen applications may not be exceeded.
- ▶ Devices with ceramic process isolating diaphragm: avoid steam hammering! Steam hammering can cause zero point drifts. Recommendation: Residue (water droplets or condensation) may remain on the process isolating diaphragm following CIP cleaning and can result in local steam hammering the next time steam cleaning takes place. In practice, drying the process isolating diaphragm (e.g. by blowing) has proved to prevent steam hammering.

Mechanical construction



For the dimensions, see the Product Configurator: www.endress.com

Search for product → click "Configuration" to the right of the product image → after configuration click "CAD"

The following dimensions are rounded values. For this reason, they may deviate slightly from the dimensions given on www.endress.com.

Design, dimensions

Device height

The device height is calculated from

- the height of the electrical connection
- the height of the housing and
- the height of the individual process connection.

The individual heights of the components are listed in the following sections. To calculate the device height simply add up the individual heights of the components. Where applicable also take into consideration the installation distance (space that is used to install the device). You can use the following table for this purpose:

Section	Page	Height	Example
Electrical connection	→ 28	(A)	
Housing height	→ 29	(B)	
Process connection height	→ 31 → 34	(C)	
Installation distance	-	(D)	

Electrical connection



A A0024426	B A0024427	C A0024428	D A0024429
Engineering unit mm (in)			

Item	Designation	Material	Weight kg (lbs)	Device	Option ¹⁾
A	M12 plug IP65 (Additional dimensions → 46)	Housing cap made of plastic	0.012 (0.03)	PMC11 PMP11	L
A	M12 plug IP65/67 (Additional dimensions → 46)	Housing cap made of plastic	0.012 (0.03)	PMC21 PMP21	M Plug connector with cable can be ordered as an accessory → 46
B	M12 plug IP66/67	Housing cap made of metal	0.030 (0.07)	PMC21 PMP21	In the case of Ex ec type of protection, the housing cap is made of metal.

Item	Designation	Material	Weight kg (lbs)	Device	Option ¹⁾
C	M16 valve plug	Plastic PPSU	0.060 (0.14)	PMC11 PMP11 PMC21 PMP21	U
C	NPT ½ valve plug	Plastic PPSU	0.060 (0.14)	PMC11 PMP11 PMC21 PMP21	V
D	Cable 5 m (16 ft)	PUR (UL94V0)	0.280 (0.62)	PMC21 PMP21	A
D	Cable 10 m (33 ft)	PUR (UL94V0)	0.570 (1.26)	PMC21 PMP21	B
D	Cable 25 m (82 ft)	PUR (UL94V0)	1.400 (3.09)	PMC21 PMP21	C

1) Product Configurator, order code for "Electrical connection"


Housing



Position	Device	Material	Weight kg (lbs)
A	PMC11 PMC21	Stainless steel 316L	0.150 (0.33)
B (up to 100 bar (1 500 psi))	PMP11 PMP21	Stainless steel 316L	0.090 (0.20)
C (400 bar (6 000 psi))	PMP11 PMP21	Stainless steel 316L	0.090 (0.20)

Process connections with internal, ceramic process membrane

Thread ISO 228 G




Device	Position	Designation	Material	Weight	Option ¹⁾
				kg (lbs)	
<ul style="list-style-type: none"> PMC11 PMC21 	A	Thread ISO 228 G 1/4" A, EN 837	316L	0.160 (0.35)	WTJ
<ul style="list-style-type: none"> PMC11 PMC21 	B	Thread ISO 228 G 1/4" (female)	316L	0.180 (0.40)	WAJ
<ul style="list-style-type: none"> PMC11 PMC21 	C	Thread ISO 228 G 1/2" A, EN 837	316L	0.180 (0.40)	WBJ
<ul style="list-style-type: none"> PMC11 PMC21 	D	Thread ISO 228 G 1/2" A, bore 11.4 mm (0.45 in)	316L	0.180 (0.40)	WWJ

1) Product Configurator, order code for "Process connection"

Process connections with
internal, ceramic process
membrane

Thread ASME




Device	Item	Designation	Material	Weight	Approval	Option ¹⁾
				kg (lbs)		
<ul style="list-style-type: none"> PMC11 PMC21 	A	ASME 1/4" MNPT, bore 3 mm (0.12 in)	316L	0.160 (0.35)	CRN	VUJ
<ul style="list-style-type: none"> PMC11 PMC21 	B	ASME 1/2" MNPT, 1/4" FNPT (female)	316L	0.190 (0.42)	CRN	VXJ
<ul style="list-style-type: none"> PMC11 PMC21 	C	ASME 1/2" MNPT, bore 11.4 mm (0.45 in)	316L	0.190 (0.42)	CRN	VWJ

1) Product Configurator, order code for "Process connection"

Process connections with
internal, ceramic process
membrane

Thread DIN13




Device	Designation	Material	Weight	Option ¹⁾
			kg (lbs)	
<ul style="list-style-type: none"> PMC11 PMC21 	DIN 13 M20 x 1.5, EN 837, bore 3 mm (0.12 in)	316L	0.180 (0.40)	X4J

1) Product Configurator, order code for "Process connection"

Process connections with
internal, ceramic process
membrane

Thread JIS B0203




Device	Designation	Material	Weight	Option ¹⁾
			kg (lbs)	
PMC21	JIS B0203 R 1/2 (male)	316L	0.180 (0.40)	ZJJ

1) Product Configurator, order code for "Process connection"

Process connections with
internal, metal process
membrane

Thread ISO 228 G




Position	Device	Description	Material	Nominal value to 100 bar (1 500 psi)			Nominal value 400 bar (6 000 psi)			Option ¹⁾
				Weight	Height C	SW/ AF	Weight	Height C	SW/ AF	
				kg (lbs)			kg (lbs)			
A	PMP11 PMP21	Thread ISO 228 G ¼" A, EN 837	316L	0.200 (0.44)	57 (2.24)	32	0.240 (0.53)	69 (2.72)	27	WTJ
B	PMP11 PMP21	Thread ISO 228 G ¼" (female)	316L	0.220 (0.49)	57 (2.24)	32	0.260 (0.57)	69 (2.72)	27	WAJ
C	PMP11 PMP21	Thread ISO 228 G ½" A, EN 837	316L	0.220 (0.49)	65 (2.56)	32	0.270 (0.60)	77 (3.03)	27	WBJ
D	PMP11 PMP21	Thread ISO 228 G ½" A, bore11.4 mm (0.45 in)	316L	0.220 (0.49)	62 (2.44)	32	0.260 (0.57)	74 (2.91)	27	WWJ

1) Product Configurator, order code for "Process connection"


Process connections with
internal, metal process
membrane

Thread ASME




Item	Device	Designation	Material	Nominal value Up to 100 bar (1 500 psi)			Nominal value 400 bar (6 000 psi)			Approval	Option ¹⁾
				Weight	Height C	SW/ AF	Weight	Height C	SW/ AF		
				kg (lbs)			kg (lbs)				
A	PMP11 PMP21	ASME ¼" MNPT, bore 3 mm (0.12 in)	316L	0.200 (0.44)	55 (2.17)	32	0.240 (0.53)	67 (2.64)	27	CRN	VUJ
B	PMP11 PMP21	ASME ½" MNPT, ¼" FNPT (female)	316L	0.230 (0.51)	67 (2.64)	32	0.260 (0.57)	79 (3.11)	27	CRN	VXJ
C	PMP11 PMP21	ASME ½" MNPT, bore 11.4 mm (0.45 in)	316L	0.230 (0.51)	67 (2.67)	32	0.270 (0.60)	79 (3.11)	27	CRN	VWJ

1) Product Configurator, order code for "Process connection"

**Process connections with
internal, metal process
membrane**
Thread DIN13


Description	Device	Material	Nominal value to 100 bar (1 500 psi)			Nominal value 400 bar (6 000 psi)			Option ¹⁾
			Weight	Height C	SW/ AF	Weight	Height C	SW/ AF	
			kg (lbs)			kg (lbs)			
DIN 13 M20 x 1.5, EN 837, bore 3 mm (0.12 in)	PMP11 PMP21	316L	0.220 (0.49)	65 (2.56)	32	0.260 (0.57)	77 (3.03)	27	X4J

1) Product Configurator, order code for "Process connection"


**Process connections with
internal, metal process
membrane**
Thread JIS B0203


Description	Device	Material	Nominal value to 100 bar (1 500 psi)			Nominal value 400 bar (6 000 psi)			Option ¹⁾
			Weight	Height C	SW/ AF	Weight	Height C	SW/ AF	
			kg (lbs)			kg (lbs)			
JIS B0203 R 1/2" (male)	PMP21	316L	0.230 (0.51)	65 (2.56)	32	0.260 (0.57)	77 (3.03)	27	ZJJ

1) Product Configurator, order code for "Process connection"


Process connections with
flush mount, metal process
membrane

Thread ISO 228 G



Device	Designation	Material	Nominal value to 100 bar (1 500 psi)			Nominal value 400 bar (6 000 psi)			Option ¹⁾
			Weight	Height C	SW/ AF	Weight	Height C	SW/ AF	
			kg (lbs)			kg (lbs)			
PMP11 PMP21	Thread ISO 228 G ½" A DIN3852, shape E	316L	0.140 (0.31)	41 (1.61)	32	0.120 (0.26)	35 (1.38)	32	WJJ

1) Product Configurator, order code for "Process connection"



Device ¹⁾	Designation	Material	Weight	Option ²⁾
			kg (lbs)	
PMP11 PMP21	Thread ISO 228 G ½" A O-ring seal, flush-mounted	316L	0.150 (0.33)	WUJ

1) Suitable for weld-in adapter 52002643 and 52010172
2) Product Configurator, order code for "Process connection"

Materials in contact with process**NOTICE**

- ▶ Device components in contact with the process are listed in the "Mechanical construction" and "Ordering information" sections.

TSE Certificate of Suitability

The following applies to all device components in contact with the process:

- They do not contain any materials derived from animals.
- No additives or operating materials derived from animals are used in production or processing.

Process connections

Endress+Hauser supplies a threaded connection made of stainless steel in accordance with AISI 316L (DIN/ EN material number 1.4404 or 1.4435). With regard to their stability-temperature property, the materials 1.4404 and 1.4435 are grouped together under 13E0 in EN 1092-1: 2001 Tab. 18. The chemical composition of the two materials can be identical.


Process isolating diaphragm

Description	Material
Ceramic process isolating diaphragm	Al ₂ O ₃ aluminum-oxide ceramic, Ceraphire® FDA, ultrapure 99.9 % (see also www.endress.com/ceraphire) The US Food & Drug Administration (FDA) has no objections to the use of ceramics made from aluminum oxide as a surface material in contact with foodstuffs. This declaration is based on the FDA certificates of our ceramic suppliers.
Metal process isolating diaphragm	AISI 316L (DIN/EN material number 1.4435)

Seals

See the specific process connection.

Materials not in contact with process Housing



Item number	Component	Material
1	Valve plug	<ul style="list-style-type: none">Seal: NBRPlug: PAScrew: V2A
2	Cable	<ul style="list-style-type: none">Pressure screw: PVDFSeal: TPE-VCable: PUR (UL 94 V0)
3	Design element	PBT/PC
4	Connection	PPSU
5	M12 plug	Plastic: PPSU
6	M12 plug	316L (1.4404) For Ex ec: metal housing cap
7	Pressure compensation element	PMP11: PBT/PC PMP21 standard: PBT/PC PMP21 with Ex ec approval: 316L (1.4404)
8	Housing	316L (1.4404)
9	Nameplates	Plastic foil (attached to housing) or directly lasered onto the housing

Filling oil

Device	Filling oil
PMP11 PMP21	Synthetic oil polyalphaolefin FDA 21 CFR 178.3620, NSF H1

Cleaning

Device	Description	Option ¹⁾
PMC11 PMP11 PMC21 PMP21	Cleaned from oil+grease	HA
PMC21	Cleaned for oxygen service	HB

1) Product Configurator, order code for "Service"

Operability

Plug-on display PHX20 (optional)

Devices with valve plug can be fitted with the optional local display PHX20.

Designation	Option ¹⁾
Plug-on display PHX20, IP65	RU



1) Product Configurator, order code for "Accessories"

A 1-line liquid crystal display (LCD) is used. The local display shows measured values, fault messages and information messages. The device display can be turned in 90° steps. Depending on the orientation of the device, it is therefore easy to read the measured values.

Technical data

Display:	4-digit, red LED display
Digit height:	7.62 mm; programmable decimal point setting
Display range:	-1999...9999
Accuracy:	0.2% of span ± 1 digit
Electrical connection:	to transmitter with 4 to 20 mA output and elbow plug DIN 43 650, with reverse polarity protection
Power supply for display:	not required, self-powered by the current loop
Voltage drop:	≤ 5 V (corresponds to load: max. 250 Ω)
Conversion rate:	3 measurements per second
Damping:	0.3 to 20 s (configurable)
Data backup:	non-volatile EEPROM
Error message:	<ul style="list-style-type: none"> ■ HI: OVERRANGING ■ LO: UNDERRANGING
Programming:	via 2 buttons, menu-guided, scaling of display range, decimal point, damping, error message
Degree of protection:	IP 65
Effect of temperature on display:	0.1% / 10 K
Electromagnetic compatibility (EMC):	Interference emission as per EN 50081, interference immunity as per EN 50082
Permitted current load:	max. 60 mA
Ambient temperature:	0 to +60 °C (+32 to +140 °F)
Housing material:	Plastic Pa6 GF30, blue Front screen made of PMMA, red
Order number:	52022914

Certificates and approvals

CE mark	The device meets the legal requirements of the relevant EC directives. Endress+Hauser that the device has been successfully tested by applying the CE mark.												
RoHS	The measuring system meets the substance restrictions of the Directive on the Restriction of the Use of Certain Hazardous Substances 2011/65/EU (RoHS 2) and the Delegated Directive (EU) 2015/863 (RoHS 3).												
RCM marking	<div>The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products bear the RCM marking on the nameplate.</div> <div></div> <div>A0029561</div>												
EAC conformity	<div>The PMC21, PMP21 and PMP23 devices meet the legal requirements of the applicable EAC directives. These are listed in the corresponding EAC Declaration of Conformity along with the standards applied.</div> <div>Endress+Hauser confirms successful testing of the device by affixing to it the EAC mark.</div>												
Approval	CSA C/US General Purpose												
Safety Instructions (XA)	<div>Safety Instructions (XA) are supplied with the device depending on the approval. The Safety Instructions are an integral part of the Operating Instructions.</div> <div> The nameplate indicates which Safety Instructions (XA) apply to the device in question.</div>												
Marine approval	<table><tr><th>Device</th><th>Name</th><th>Option ¹⁾</th></tr><tr><td>PMC21 PMP21</td><td>DNV GL</td><td>LE</td></tr><tr><td>PMC21 PMP21</td><td>ABS</td><td>LF</td></tr><tr><td>PMC21 PMP21</td><td>RINA</td><td>LV</td></tr></table> <div>1) Product Configurator, order code for "Additional approval"</div>	Device	Name	Option ¹⁾	PMC21 PMP21	DNV GL	LE	PMC21 PMP21	ABS	LF	PMC21 PMP21	RINA	LV
Device	Name	Option ¹⁾											
PMC21 PMP21	DNV GL	LE											
PMC21 PMP21	ABS	LF											
PMC21 PMP21	RINA	LV											
Pressure Equipment Directive 2014/68/EU (PED)	<div>Pressure equipment with permitted pressure ≤ 200 bar (2 900 psi)</div> <div>Pressure equipment (maximum working pressure PS ≤ 200 bar (2 900 psi)) can be classified as pressure accessories in accordance with Pressure Equipment Directive 2014/68/EU. If the maximum working pressure is ≤ 200 bar (2 900 psi) and the pressurized volume of the pressure equipment is ≤ 0.1 l, the pressure equipment is subject to the Pressure Equipment Directive (see Pressure Equipment Directive 2014/68/EU, Article 4, point 3). The Pressure Equipment Directive only requires that the pressure equipment shall be designed and manufactured in accordance with the “sound engineering practice of a Member State”.</div> <div>Reasons:</div> <div><ul style="list-style-type: none">■ Pressure Equipment Directive 2014/68/EU Article 4, point 3■ Pressure Equipment Directive 2014/68/EU, Commission's Working Group "Pressure", Guideline A-05 + A-06</div>												

Note:

A separate assessment must be performed for pressure equipment that is part of a safety instrumented system intended to protect a pipe or vessel from exceeding allowable limits (equipment with safety function in accordance with Pressure Equipment Directive 2014/68/EU, Article 2, point 4).

Pressure equipment with allowable pressure > 200 bar (2 900 psi)

Pressure equipment intended for use in any process fluid and having a pressurized volume of < 0.1 l and a maximum allowable pressure PS > 200 bar (2 900 psi) must satisfy the essential safety requirements set out in Annex I of the Pressure Equipment Directive 2014/68/EU. According to Article 13, pressure equipment must be classified into categories in accordance with Annex II. Taking into account the small volume specified above, the pressure equipment can be categorized into Category I. They must then bear a CE mark.

Reasons:

- Pressure Equipment Directive 2014/68/EU, Article 13, Annex II
- Pressure Equipment Directive 2014/68/EU, Commission's Working Group "Pressure", Guideline A-05

Note:

A separate assessment must be performed for pressure equipment that is part of a safety instrumented system intended to protect a pipe or vessel from exceeding allowable limits (equipment with safety function in accordance with Pressure Equipment Directive 2014/68/EU, Article 2, point 4).

The following also applies:

PMP21 with threaded connection and internal membrane PN > 200 :

Suitable for stable gases in group 1, category I, module A

External standards and guidelines

The applicable European guidelines and standards can be found in the relevant EU Declarations of Conformity. The following standards were also applied:

DIN EN 60770 (IEC 60770):

Transmitters for use in industrial process control systems Part 1: Methods for performance evaluation

Methods for evaluating the performance of transmitters for control and regulation in industrial process control systems.

DIN 16086:

Electrical pressure measuring instruments, pressure sensors, pressure transmitters, pressure measuring instruments, concepts, specifications in data sheets

Procedure for writing specifications in data sheets for electrical pressure measuring instruments, pressure sensors and pressure transmitters.

EN 61326-X:

EMC product family standard for electrical equipment for measurement, control, regulation and laboratory procedures.

EN 60529:

Degrees of protection provided by enclosure (IP code)

NAMUR - User association of automation technology in process industries.

NE21 - Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment.

NE 43 - Standardization of the Signal Level for the Failure Information of Digital Transmitters.

NE44 - Standardization of Status Indicators on PCT Instruments with the Help of Light Emitting Diodes

NE53 - Software of Field Devices and Signal-processing Devices with Digital Electronics

CRN approval

Some device versions have CRN approval. A CRN-approved process connection with a CSA approval must be ordered for a CRN-approved device. The CRN-approved devices are assigned the registration number 0F18141.5C.

Ordering information: Product Configurator, order code for "Process connection" (the CRN process connections are indicated appropriately in the "Mechanical construction" section.)

Calibration unit

Name	Option ¹⁾
Sensor range; %	A
Sensor range; mbar/bar	B
Sensor range; kPa/MPa	C
Sensor range; psi	F
Customer-specific; see additional spec.	J

1) Product Configurator, order code for "Calibration; unit"

Calibration

Name	Option ¹⁾
3-point calibration certificate ²⁾	F3

1) Product Configurator, order code for "Calibration"

2) No final test report for PNP outputs.

Inspection certificates

Device	Name	Option ¹⁾
PMC21 PMP21	3.1 Material documentation, wetted metal parts, EN10204-3.1 inspection certificate	YES

1) Product Configurator, order code for "Test, Certificate"



Documentation currently available on the Endress+Hauser website: www.endress.com → Downloads or with the serial number of the device under Online Tools in the Device Viewer.

Service

- Cleaned of oil+grease (wetted)
- Checked, cleaned for oxygen application
- Min. alarm current set

Product documentation on paper

A printed (hard copy) version of test reports, declarations and inspection certificates can optionally be ordered via order code 570 "Service", option I7 "Product documentation on paper". The documents are then provided with the device upon delivery.

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate" -> Select your country -> Click "Products" -> Select the product using the filters and search field -> Open product page -> The "Configure" button to the right of the product image opens the Product Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

**Product Configurator - the tool for individual product configuration**

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Scope of delivery

- Measuring device
- Optional accessories
- Brief Operating Instructions
- Certificates

Accessories

Weld-in adapter

Various weld-in adapters are available for installation in vessels or pipes.

Device	Description	Option ¹⁾	Order number
PMP21	Weld-in adapter G½, 316L	QA	52002643
PMP21	Weld-in adapter G½, 316L 3.1 EN10204-3.1 material, inspection certificate	QB	52010172
PMP21	Weld-in tool adapter G½, brass	QC	52005082
PMP21	Weld-in adapter G1/2, 316L, for G1/2 A DIN 3852	QM	71389241
PMP21	Weld-in adapter G1/2, 316L, 3.1, for G1/2 A DIN 3852, EN10204-3.1 material, inspection certificate	QN	71389243




1) Product Configurator, order code for "Accessory enclosed"

If installed horizontally and weld-in adapters with a leakage hole are used, ensure that the leakage hole is pointing down. This allows leaks to be detected as quickly as possible.

Plug-on display PHX20


→ 41

M12 plug-in jack

Plug	Degree of protection	Material	Option ¹⁾	Order number
M12 (self-terminated connection at M12 plug) 	IP67	<ul style="list-style-type: none"> Union nut: Cu Sn/Ni Body: PBT Seal: NBR 	R1	52006263
M12 90 degrees with 5m (16 ft) cable 	IP67	<ul style="list-style-type: none"> Union nut: GD Zn/Ni Body: PUR Cable: PVC Cable colors <ul style="list-style-type: none"> 1 = BN = brown 2 = WT = white 3 = BU = blue 4 = BK = black 	RZ	52010285
M12 90 degrees (self-terminated connection at M12 plug) 	IP67	<ul style="list-style-type: none"> Union nut: GD Zn/Ni Body: PBT Seal: NBR 	RM	71114212

1) Product Configurator, order code for "Accessory enclosed"

Supplemental documentation

Field of activities	Pressure measurement, powerful measuring instruments for process pressure, differential pressure, level and flow: FA00004P
Technical Information	<ul style="list-style-type: none">■ TI00241F: EMC Test Procedures■ TI00426F: Weld-in adapters, process adapters and flanges (overview)
Safety Instructions (XA)	<p>Safety Instructions (XA) are supplied with the device depending on the approval. The Safety Instructions are an integral part of the Operating Instructions.</p> <p> The nameplate indicates which Safety Instructions (XA) apply to the device in question.</p>



www.addresses.endress.com
