# Technical Information **Proline Promag H 200**

Electromagnetic flowmeter



# The measuring device for smallest flow rates with genuine two-wire technology

# Application

- The measuring principle is virtually independent of pressure, density, temperature and viscosity
- For the smallest flow quantities and demanding hygienic applications

# Device properties

- Liner made of PFA
- Sensor housing made of stainless steel (3A, EHEDG)
- Wetted materials CIP, SIP cleanable
- Loop-powered technology
- Robust two-chamber housing
- Plant safety: worldwide approvals (SIL, Haz. area)

# Your benefits

- Flexible installation concept numerous hygienic process connections
- Energy-saving flow measurement no pressure loss due to cross-section constriction
- Maintenance-free no moving parts
- Convenient device wiring separate connection compartment
- Safe operation no need to open the device due to display with touch control, background lighting
- Integrated verification Heartbeat Technology™



# Table of contents

Document information	
Symbols used	3
Function and system design	3
Measuring principle	
Measuring system	. 5
Safety	5
Input	. 5
Measured variable	
Measuring range	
Operable flow range	6
Output	6
Output signal	-
Signal on alarm	
Load	
Ex connection data	9
Low flow cut off	13
Galvanic isolation	13
Protocol-specific data	13
Power supply	17
Terminal assignment	17
Pin assignment, device plug	18
Supply voltage	18
Power consumption	18
Current consumption	19
Power supply failure	19
Electrical connection	19 23
Potential equalization	23 24
Terminals	24
Cable specification	24
Overvoltage protection	25
Performance characteristics	25
Reference operating conditions	25
Maximum measured error	25
Repeatability	26
Influence of ambient temperature	26
Installation	26
Mounting location	27
Orientation	27
Inlet and outlet runs	28
Adapters	28
Special mounting instructions	29
Environment	29
Ambient temperature range	29
Storage temperature	30
Degree of protection	30
Shock resistance	30
Vibration resistance	30 30
Electromagnetic compatibility (EMC)	30
J 1 J 1 J	

Process . Medium temperature range . Conductivity . Pressure-temperature ratings . Pressure tightness . Flow limit . Pressure loss . System pressure . Vibrations .	<b>30</b> 31 31 34 34 34 35 35
Mechanical construction	<b>35</b> 48 57 57 58 59 59 59
Operability	60 60 61 63
Certificates and approvals CE mark C-Tick symbol Ex approval Sanitary compatibility Functional safety HART certification FOUNDATION Fieldbus certification Certification PROFIBUS Other standards and guidelines	64 64 64 65 65 65 65 65
Ordering information	66
Application packages	<b>66</b> 66 66
Accessories	<b>67</b> 67 68 68 69
Documentation	<b>69</b> 69 70
Registered trademarks	70

# **Document information**

# Symbols used

# **Electrical symbols**

Symbol	Meaning	Symbol	Meaning
	Direct current	$\sim$	Alternating current
$\sim$	Direct current and alternating current	<u>+</u>	<b>Ground connection</b> A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	<b>Protective ground connection</b> A terminal which must be connected to ground prior to establishing any other connections.	Ą	<b>Equipotential connection</b> A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice.

# Symbols for certain types of information

Symbol	Meaning
	<b>Permitted</b> Procedures, processes or actions that are permitted.
	<b>Preferred</b> Procedures, processes or actions that are preferred.
	<b>Forbidden</b> Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
Ĩ	Reference to documentation
	Reference to page
	Reference to graphic
	Visual inspection


# Symbols in graphics

Symbol	Meaning	Symbol	Meaning
1, 2, 3,	Item numbers	1. , 2. , 3	Series of steps
A, B, C,	Views	A-A, B-B, C-C,	Sections
EX	Hazardous area	$\bigotimes$	Safe area (non-hazardous area)
≈➡	Flow direction		

# Function and system design

Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



- Ue Induced voltage
- *B Magnetic induction (magnetic field)*
- L Electrode spacing
- I Current
- v Flow velocity

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced  $(U_e)$  is proportional to the flow velocity (v) and is supplied to the amplifier by means of two measuring electrodes. The flow volume (Q) is calculated via the pipe cross-section (A). The DC magnetic field is created through a switched direct current of alternating polarity.

# Formulae for calculation


- Induced voltage  $U_e = B \cdot L \cdot v$
- Volume flow  $Q = A \cdot v$

# Measuring system

The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.

## Transmitter



### Sensor

Promag H	Nominal diameter range: DN 2 to 25 (1/12 to 1")
A0017702	<ul> <li>Materials:</li> <li>Sensor housing: stainless steel 1.4301 (304)</li> <li>Measuring tubes: stainless steel, 1.4301 (304)</li> <li>Liner: PFA (USP Class VI; FDA 21 CFR 177.1550; 3A)</li> <li>Electrodes: stainless steel 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022); tantalum; platinum</li> <li>Process connections: stainless steel, 1.4404 (F316L); PVDF; PVC adhesive sleeve</li> <li>Seals: EPDM, FKM, Kalrez</li> <li>Grounding rings (only for DN 02 to 25 (1/12 to 1")): stainless steel, 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022); tantalum</li> </ul>

## Safety

## IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

0,5

2

0.005

0.025

# Input

2

4

1/12

1/8

### Measured variable Direct measured variables Volume flow (proportional to induced voltage) **Calculated measured variables** Mass flow Measuring range Typically v = 0.01 to 10 m/s (0.03 to 33 ft/s) with the specified accuracy Flow characteristic values in SI units Nominal Recommended Factory settings diameter flow Full scale value current Min./max. full scale value Pulse value Low flow cut off output (v ~ 0.04 m/s) (v ~ 0.3/10 m/s) (~ 2 pulse/s) (v ~ 2.5 m/s) [mm] [dm<sup>3</sup>/min] [dm<sup>3</sup>/min] [dm<sup>3</sup>/min] [in] [dm<sup>3</sup>]

0.06 to 1.8

0.25 to 7

0.01

0.05

	iinal ieter	Recommended flow	Factory settings		
Min./max. full scale value (v ~ 0.3/10 m/s)			Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 2 pulse/s)	Low flow cut off (v ~ 0.04 m/s)
[mm]	[in]	[dm³/min]	[dm <sup>3</sup> /min]	[dm <sup>3</sup> ]	[dm³/min]
8	3/8	1 to 30	8	0.1	0.1
5		1 00 9 0	0	0.1	-,-
15	1/2	4 to 100	25	0.2	0,5

Flow characteristic values in US units

Nom diam	ninal neter	Recommended flow	Factory settings		
		Min./max. full scale value (v ~ 0.3/10 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 2 pulse/s)	Low flow cut off (v ~ 0.04 m/s)
[in]	[mm]	[gal/min]	[gal/min]	[gal]	[gal/min]
1/12	2	0.015 to 0.5	0,1	0,001	0,002
1/8	4	0.07 to 2	0,5	0,005	0,008
3/8	8	0.25 to 8	2	0,02	0,025
1/2	15	1 to 27	6	0,05	0,1
1	25	2.5 to 80	18	0,2	0,25

To calculate the measuring range, use the Applicator sizing tool  $\rightarrow \square 68$ 

# Recommended measuring range

"Flow limit" section  $\rightarrow$  🗎 34

Operable flow range

Over 1000 : 1

# Output

Output signal

# Current output

Current output	4-20 mA HART (passive)
Resolution	< 1 µA
Damping	Adjustable: 0.0 to 999.9 s
Assignable measured variables	<ul><li>Volume flow</li><li>Mass flow</li></ul>

# Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	<ul> <li>DC 35 V</li> <li>50 mA</li> <li>for information on the Ex connection values → ● 9</li> </ul>

Voltage drop	<ul> <li>For ≤ 2 mA: 2 V</li> <li>For 10 mA: 8 V</li> </ul>
Residual current	≤ 0.05 mA
Pulse output	
Pulse width	Adjustable: 5 to 2 000 ms
Maximum pulse rate	100 Impulse/s
Pulse value	Adjustable
Assignable measured variables	<ul><li>Volume flow</li><li>Mass flow</li></ul>
Frequency output	
Output frequency	Adjustable: 0 to 1 000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	<ul><li>Volume flow</li><li>Mass flow</li></ul>
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	<ul> <li>Off</li> <li>On</li> <li>Diagnostic behavior</li> <li>Limit value <ul> <li>Volume flow</li> <li>Mass flow</li> </ul> </li> <li>Flow direction monitoring</li> <li>Status <ul> <li>Empty pipe detection</li> <li>Low flow cut off</li> </ul> </li> </ul>

# FOUNDATION Fieldbus

Signal encoding	Manchester Bus Powered (MBP)
Data transfer	31.25 KBit/s, Voltage mode

# PROFIBUS PA

Signal encoding	Manchester Bus Powered (MBP)
Data transfer	31.25 KBit/s, Voltage mode

# Signal on alarm

Depending on the interface, failure information is displayed as follows:

# **Current output**

HART

Device diagnostics	Device condition can be read out via HART Command 48
--------------------	--

# Pulse/frequency/switch output

# Pulse output

Failure mode	Choose from: • Actual value • No pulses
--------------	---

# Frequency output

Failure mode	Choose from: • Actual value • 0 Hz
	<ul> <li>Defined value: 0 to 1250 Hz</li> </ul>

# Switch output

Failure mode	Choose from:
	Current status
	• Open
	Closed

# **FOUNDATION Fieldbus**

Status and alarm messages	Diagnostics in accordance with FF-912
Error current FDE (Fault Disconnection Electronic)	0 mA

# PROFIBUS PA

Status and alarm messages	Diagnostics in accordance with PROFIBUS PA Profile 3.02
Error current FDE (Fault Disconnection Electronic)	0 mA

# Local display

Plain text display	With information on cause and remedial measures	
Backlight	Additionally for device version with SD03 local display: red lighting indicates a device error.	

Status signal as per NAMUR recommendation NE 107

# Operating tool

- Via digital communication:
  - HART protocol
  - FOUNDATION Fieldbus
  - PROFIBUS PA
- Via service interface

# Plain text display

With information on cause and remedial measures

Additional information on remote operation  $\rightarrow \cong 61$ 


# Load

Load for current output: 0 to 500  $\Omega,$  depending on the external supply voltage of the power supply unit

# Calculation of the maximum load

Depending on the supply voltage of the power supply unit ( $U_S$ ), the maximum load ( $R_B$ ) including line resistance must be observed to ensure adequate terminal voltage at the device. In doing so, observe the minimum terminal voltage

- For  $U_S = 18$  to 18.9 V:  $R_B \le (U_S 18 \text{ V})$ : 0.0036 A
- For  $U_S = 18.9$  to 24.5 V:  $R_B \le (U_S 13.5 \text{ V})$ : 0.022 A
- For  $U_S = 24.5$  to 30 V:  $R_B \le 500 \Omega$



- 1 Operating range
- 1.1 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with Ex i
- 1.2 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with non-Ex and Ex d

### Sample calculation

Supply voltage of the power supply unit:  $U_S$  = 19 V Maximum load:  $R_B \leq$  (19 V - 13.5 V): 0.022 A = 250  $\Omega$ 

# Ex connection data

## Safety-related values

Type of protection Ex d

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	U <sub>nom</sub> = DC 35 V U <sub>max</sub> = 250 V
Option <b>B</b>	4-20mA HART	U <sub>nom</sub> = DC 35 V U <sub>max</sub> = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option <b>E</b>	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$

Order code for "Output"	Output type	Safety-related values
Option <b>G</b>		$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
		$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$

1) Internal circuit limited by  $R_i = 760.5 \Omega$ 

# Ex nA type of protection

Order code for "Output"	Output type	Safety-related values
Option <b>A</b>	4-20mA HART	$U_{nom} = DC 35 V$ $U_{max} = 250 V$
Option <b>B</b>	4-20mA HART	$U_{nom} = DC 35 V$ $U_{max} = 250 V$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	

1) Internal circuit limited by  $R_i$  = 760.5  $\Omega$ 

# *Type of protection XP*

Order code for "Output"	Output type	Safety-related values
Option <b>A</b>	4-20mA HART	U <sub>nom</sub> = DC 35 V U <sub>max</sub> = 250 V
Option <b>B</b>	4-20mA HART	U <sub>nom</sub> = DC 35 V U <sub>max</sub> = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
Option <b>E</b>	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$\begin{array}{l} U_{nom} = DC \ 35 \ V \\ U_{max} = 250 \ V \\ P_{max} = 1 \ W^{1)} \end{array}$

Order code for "Output"	Output type	Safety-related values
Option <b>G</b>	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$

1) Internal circuit limited by  $R_i = 760.5 \Omega$ 

# Intrinsically safe values

Type of protection Ex ia

Order code for "Output"	Output type	Intrinsically safe	values
Option A	4-20mA HART	$\begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 5 \; nF \end{array}$	
Option <b>B</b>	4-20mA HART	$\begin{array}{l} U_i = DC \; 30 \; V \\ I_i = 300 \; mA \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 5 \; nF \end{array}$	
	Pulse/frequency/switch output	$\begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 6 \; nF \end{array}$	
Option E	FOUNDATION Fieldbus	$STANDARD \\ U_i = 30 V \\ I_i = 300 mA \\ P_i = 1.2 W \\ L_i = 10 \mu H \\ C_i = 5 nF$	FISCO $U_i = 17.5 V$ $I_i = 550 mA$ $P_i = 5.5 W$ $L_i = 10 \mu H$ $C_i = 5 nF$
	Pulse/frequency/switch output		
Option <b>G</b>	PROFIBUS PA		$      FISCO \\ U_i = 17.5 V \\ I_i = 550 mA \\ P_i = 5.5 W \\ L_i = 10 \ \mu H \\ C_i = 5 nF $
	Pulse/frequency/switch output	$ \begin{array}{l} U_i = 30 \ V \\ l_i = 300 \ mA \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array} $	

# Type of protection Ex ic

Order code for "Output"	Output type	Intrinsically safe	values
Option <b>A</b>	4-20mA HART	$ \begin{array}{l} U_{i} = DC \; 35 \; V \\ I_{i} = n.a. \\ P_{i} = 1 \; W \\ L_{i} = 0 \; \mu H \\ C_{i} = 5 \; nF \end{array} $	
Option <b>B</b>	4-20mA HART	$ \begin{array}{l} U_i = DC \; 35 \; V \\ I_i = n.a. \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 5 \; n F \end{array} $	
	Pulse/frequency/switch output	$\begin{array}{l} U_{i} = DC \; 35 \; V \\ I_{i} = n.a. \\ P_{i} = 1 \; W \\ L_{i} = 0 \; \mu H \\ C_{i} = 6 \; nF \end{array}$	
Option <b>E</b>	FOUNDATION Fieldbus	$\label{eq:standard} \begin{array}{l} STANDARD\\ U_i = 32 \ V\\ l_i = 300 \ mA\\ P_i = n.a.\\ L_i = 10 \ \mu H\\ C_i = 5 \ nF \end{array}$	$\label{eq:FISCO} \begin{split} FISCO & \\ U_i = 17.5 \ V & \\ l_i = n.a. & \\ P_i = n.a. & \\ L_i = 10 \ \mu H & \\ C_i = 5 \ nF & \end{split}$
	Pulse/frequency/switch output	$\begin{array}{l} U_{i} = 35 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$	
Option <b>G</b>	PROFIBUS PA	$      STANDARD \\ U_i = 32 V \\ l_i = 300 mA \\ P_i = n.a. \\ L_i = 10 \ \mu H \\ C_i = 5 \ nF $	$      FISCO \\ U_i = 17.5 V \\ l_i = n.a. \\ P_i = n.a. \\ L_i = 10 \ \mu H \\ C_i = 5 \ nF $
	Pulse/frequency/switch output	$\begin{array}{l} U_{i} = 35 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$	

# Type of protection IS

Order code for "Output"	Output type	Intrinsically safe values
Option <b>A</b>	4-20mA HART	$ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 5 \; nF \end{array} $
Option <b>B</b>	4-20mA HART	$ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 5 \; nF \end{array} $
	Pulse/frequency/switch output	$ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 6 \; nF \end{array} $

Order code for "Output"	Output type	Intrinsically safe	values
Option E	FOUNDATION Fieldbus		$      FISCO \\ U_i = 17.5 V \\ l_i = 550 mA \\ P_i = 5.5 W \\ L_i = 10 \ \mu H \\ C_i = 5 nF $
	Pulse/frequency/switch output	$\begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$	
Option <b>G</b>	PROFIBUS PA		$      FISCO \\ U_i = 17.5 V \\ l_i = 550 mA \\ P_i = 5.5 W \\ L_i = 10 \ \mu H \\ C_i = 5 \ nF $
	Pulse/frequency/switch output	$\begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$	

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

All outputs are galvanically isolated from one another.

HART

# Protocol-specific data

Manufacturer ID	0x11
Device type ID	0x48
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	<ul> <li>Min. 250 Ω</li> <li>Max. 500 Ω</li> </ul>
Dynamic variables	<ul> <li>Read out the dynamic variables: HART command 3</li> <li>The measured variables can be freely assigned to the dynamic variables.</li> <li>Measured variables for PV (primary dynamic variable)</li> <li>Off</li> <li>Volume flow</li> <li>Mass flow</li> </ul>
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable) • Volume flow • Mass flow • Totalizer 1 • Totalizer 2 • Totalizer 3
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned.

# FOUNDATION Fieldbus

Manufacturer ID	0x452B48
Ident number	0x1048
Device revision	1

DD revision	Information and files under:
CFF revision	<ul><li>www.endress.com</li><li>www.fieldbus.org</li></ul>
Device Tester Version (ITK version)	6.1.1
ITK Test Campaign Number	IT094200
Link Master capability (LAS)	Yes
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device
Node address	Factory setting: 247 (0xF7)
Supported functions	The following methods are supported: • Restart • ENP Restart • Diagnostic
Virtual Communication Relation	nships (VCRs)
Number of VCRs	44
Number of link objects in VFD	50
Permanent entries	1
Client VCRs	0
Server VCRs	10
Source VCRs	43
Sink VCRs	0
Subscriber VCRs	43
Publisher VCRs	43
Device Link Capabilities	
Slot time	4
Min. delay between PDU	8
Max. response delay	Min. 5

# Transducer Blocks

Block	Contents	Output values
Setup Transducer Block (TRDSUP)	All parameters for standard commissioning.	No output values
Advanced Setup Transducer Block (TRDASUP)	All parameters for more accurate measurement configuration.	No output values
Display Transducer Block (TRDDISP)	Parameters for configuring the local display.	No output values
HistoROM Transducer Block (TRDHROM)	Parameters for using the HistoROM function.	No output values
Diagnostic Transducer Block (TRDDIAG)	Diagnostics information.	Process variables (AI Channel) • Temperature (7) • Volume flow (9) • Mass flow (11)
Expert Configuration Transducer Block (TRDEXP)	Parameters that require the user to have in- depth knowledge of the operation of the device in order to configure the parameters appropriately.	No output values

Block	Contents	Output values
Expert Information Transducer Block (TRDEXPIN)	Parameters that provide information about the state of the device.	No output values
Service Sensor Transducer Block (TRDSRVS)	Parameters that can only be accessed by Endress +Hauser Service.	No output values
Service Information Transducer Block (TRDSRVIF)	Parameters that provide Endress+Hauser Service with information about the state of the device.	No output values
Total Inventory Counter Transducer Block (TRDTIC)	Parameters for configuring all the totalizers and the inventory counter.	Process variables (AI Channel) • Totalizer 1 (16) • Totalizer 2 (17) • Totalizer 3 (18)
Heartbeat Technology Transducer Block (TRDHBT)	Parameters for the configuration and comprehensive information about the results of the verification.	No output values
Heartbeat Results 1 Transducer Block (TRDHBTR1)	Information about the results of the verification.	No output values
Heartbeat Results 2 Transducer Block (TRDHBTR2)	Information about the results of the verification.	No output values
Heartbeat Results 3 Transducer Block (TRDHBTR3)	Information about the results of the verification.	No output values
Heartbeat Results 4 Transducer Block (TRDHBTR4)	Information about the results of the verification.	No output values

# Function blocks

Block	Number of blocks	Contents	Process variables (Channel)
Resource Block (RB)	1	This Block (extended functionality) contains all the data that uniquely identify the device; it is the equivalent of an electronic nameplate for the device.	-
Analog Input Block (AI)	4	This Block (extended functionality) receives the measurement data provided by the Sensor Block (can be selected via a channel number) and makes the data available for other blocks at the output.	<ul><li>Process variables (AI Channel)</li><li>Temperature (7)</li><li>Volume flow (9)</li><li>Mass flow (11)</li></ul>
		Execution time: 25 ms	
Discrete Input Block (DI)	2	This Block (standard functionality) receives a discrete value (e.g. indicator that measuring range has been exceeded) and makes the value available for other blocks at the output. <b>Execution time:</b> 19 ms	<ul> <li>Switch output state (101)</li> <li>Empty pipe detection (102)</li> <li>Low flow cut off (103)</li> <li>Status verification (105)</li> </ul>
PID Block (PID)	1	This Block (standard functionality) acts as a proportional-integral-differential controller and can be used universally for control in the field. It enables cascading and feedforward control.	-
		Execution time: 25 ms	

Block	Number of blocks	Contents	Process variables (Channel)
Multiple Digital Output Block (MDO)	1	This Block (standard functionality) receives several discrete values and makes them available for other blocks at the output. <b>Execution time:</b> 19 ms	Channel_DO (122)  Value 1: Reset totalizer 1 Value 2: Reset totalizer 2 Value 3: Reset totalizer 3 Value 4: Flow override Value 5: Start heartbeat verification Value 6: Status switch output Value 7: Not assigned Value 8: Not assigned
Integrator Block (IT)	1	This Block (standard functionality) integrates a measured variable over time or totalizes the pulses from a Pulse Input Block. The Block can be used as a totalizer that totalizes until a reset, or as a batch totalizer whereby the integrated value is compared against a target value generated before or during the control routine and generates a binary signal when the target value is reached. <b>Execution time:</b> 21 ms	_

# PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x1563
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: • www.endress.com • www.profibus.org
Output values (from measuring device to automation system)	Analog input 1 to 2 Mass flow Volume flow Digital input 1 to 2 Empty pipe detection Low flow cut off Status switch output Status verification
	Totalizer 1 to 3 Mass flow Volume flow Corrected volume flow
Input values (from automation system to measuring device)	Digital output 1 to 3 (fixed assignment) Digital output 1: switch positive zero return on/off Digital output 2: switch switch output on/off Digital output 3: start verification Totalizer 1 to 3 Totalize Reset and hold Preset and hold Operating mode configuration: - Net flow total - Forward flow total - Reverse flow total


Supported functions	<ul> <li>Identification &amp; Maintenance Simplest device identification on the part of the control system and nameplate</li> <li>PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download</li> <li>Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur</li> </ul>
Configuration of the device address	<ul> <li>DIP switches on the I/O electronics module</li> <li>Local display</li> <li>via operating tools (e.g. FieldCare)</li> </ul>

# Power supply

# Terminal assignment

# Transmitter

### Connection versions



Ground terminal for cable shield

Order code for "Output"	Terminal numbers			
	Outŗ	put 1	Out	put 2
	1 (+)	2 (-)	3 (+)	4 (-)
Option <b>A</b>	4-20 mA HA	ART (passive)		_
Option <b>B</b> $^{1)}$	4-20 mA HA	ART (passive)		y/switch output sive)
Option $\mathbf{E}^{(1)(2)}$	FOUNDATION Fieldbus		· ·	y/switch output sive)
Option $\mathbf{G}^{(1)(3)}$	PROFII	BUS PA	- ·	y/switch output sive)

1) Output 1 must always be used; output 2 is optional.

2) 3) FOUNDATION Fieldbus with integrated reverse polarity protection.

PROFIBUS PA with integrated reverse polarity protection.

# Pin assignment, device plug

# PROFIBUS PA

Device plug for signal transmission (device side)

	Pin		Assignment	Coding	Plug/socket
	1	+	PROFIBUS PA +	А	Plug
	2		Grounding		
A0019021	3	-	PROFIBUS PA -		
	4		Not assigned		

## FOUNDATION Fieldbus

Device plug for signal transmission (device side)

	Pin		Assignment	Coding	Plug/socket
	1	+	Signal +	А	Plug
	2	-	Signal –		
A0019021	3		Not assigned		
	4		Grounding		

# Supply voltage

# Transmitter

An external power supply is required for each output.

Order code for "Output"	Minimum terminal voltage	Maximum terminal voltage
Option <b>A</b> <sup>1) 2)</sup> : 4-20 mA HART	<ul> <li>For 4 mA: ≥ DC 18 V</li> <li>For 20 mA: ≥ DC 14 V</li> </ul>	DC 35 V
Option <b>B</b> <sup>1) 2)</sup> : 4-20 mA HART, pulse/frequency/ switch output	<ul> <li>For 4 mA: ≥ DC 18 V</li> <li>For 20 mA: ≥ DC 14 V</li> </ul>	DC 35 V
Option <b>E</b> <sup>3)</sup> : FOUNDATION Fieldbus, pulse/ frequency/switch output	≥ DC 9 V	DC 32 V
Option <b>G</b> <sup>3)</sup> : PROFIBUS PA, pulse/frequency/switch output	≥ DC 9 V	DC 32 V

1) External supply voltage of the power supply unit with load.

 For device versions with SD03 local display: The terminal voltage must be increased by DC 2 V if backlighting is used.

3) For device version with SD03 local display: The terminal voltage must be increased by DC 0.5 V if backlighting is used.

For information about the load see  $\rightarrow \cong 9$ 

Various power supply units can be ordered from Endress+Hauser: see "Accessories" section  $\rightarrow \cong 69$ 

For information on the Ex connection values  $\rightarrow \cong 9$ 

### Power consumption

Transmitter

Order code for "Output"	Maximum power consumption
Option A: 4-20 mA HART	770 mW
Option <b>B</b> : 4-20 mA HART, pulse/ frequency/switch output	<ul><li>Operation with output 1: 770 mW</li><li>Operation with output 1 and 2: 2 770 mW</li></ul>


	Order code for "Output"	Maximum power consumption		
	Option <b>E</b> : FOUNDATION Fieldbus, pulse/ frequency/switch output	<ul><li>Operation with output 1: 576 mW</li><li>Operation with output 1 and 2: 2 576 mW</li></ul>		
	Option <b>G</b> : PROFIBUS PA, pulse/frequency/ switch output	<ul><li>Operation with output 1: 512 mW</li><li>Operation with output 1 and 2: 2512 mW</li></ul>		
Current consumption	For information on the Ex connecti	on values → 🗎 9		
current consumption	For every 4-20 mA or 4-20 mA HART c	$\alpha$		
	If the option <b>Defined value</b> is selected in the <b>Failure mode</b> parameter : 3.59 to 22.5 mA			
	PROFIBUS PA			
	16 mA			
	FOUNDATION Fieldbus			

16 mA

Power supply failure	<ul> <li>Totalizers stop at the last value measured.</li> </ul>
	<ul> <li>Configuration is retained in the device memory (HistoROM).</li> <li>Error messages (incl. total operated hours) are stored.</li> </ul>
	,,, _,, _

**Electrical connection** 


# Connecting the transmitter



Cable entry for output 1 Cable entry for output 2 1 2

# **Connection examples**


Current output 4-20 mA HART




■ 1 Connection example for 4-20 mA HART current output (passive)

- Observe the maximum load  $\rightarrow \bigcirc 9$ 3 Cable shield, observe cable specifications
- 4 Analog display unit: observe maximum load  $\rightarrow \cong 9$
- 5 Transmitter


## Pulse/frequency output






- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- *3* Transmitter: observe input values  $\rightarrow \bigoplus 6$

# Switch output



- ☑ 3 Connection example for switch output (passive)
- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: observe input values


# PROFIBUS-PA



- € 4 Connection example for PROFIBUS-PA
- Control system (e.g. PLC) Segment coupler PROFIBUS DP/PA Cable shield
- 1 2 3 4 5
- T-box
- Measuring device
- 6 7 Local grounding Bus terminator
- 8 Potential matching line

Endress+Hauser


# FOUNDATION Fieldbus



🛃 5 Connection example for FOUNDATION Fieldbus

- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus) 2
- 3 Cable shield
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line

# HART input




### 🖸 6 Connection example for HART input with a common negative

- Automation system with HART output (e.g. PLC) 1
- 2 *Resistor for HART communication* ( $\geq 250 \Omega$ ): *observe maximum load*  $\rightarrow \square 9$
- 3 Active barrier for power supply (e.g. RN221N) 4
- Cable shield, observe cable specifications
- Analog display unit: observe maximum load  $\rightarrow \cong 9$ 5
- 6 Pressure transmitter (e.g. Cerabar M, Cerabar S): see requirements
- 7 Transmitter

Potential equalization	Requirements
	<ul> <li>Please consider the following to ensure correct measurement:</li> <li>Same electrical potential for the fluid and sensor</li> <li>Company-internal grounding concepts</li> <li>Pipe material and grounding</li> </ul>
	For devices intended for use in hazardous locations, please observe the guidelines in the Ex documentation (XA).
	Connection example, standard scenario
	Metal process connections
	Potential equalization is generally via the metal process connections that are in contact with the medium and mounted directly on the sensor. Therefore there is generally no need for additional potential equalization measures.
	Connection example in special situations
	Plastic process connections
	In the case of plastic process connections, additional grounding rings or process connections with an integrated grounding electrode must be used to ensure potential matching between the sensor and the fluid. If there is no potential matching, this can affect the measuring accuracy or cause the destruction of the sensor as a result of the electrochemical decomposition of the electrodes.
	<ul> <li>Note the following when using grounding rings:</li> <li>Depending on the option ordered, plastic disks are used instead of grounding rings on some process connections. These plastic disks only act as "spacers" and do not have any potential matching function. Furthermore, they also perform a significant sealing function at the sensor/ connection interface. Therefore, in the case of process connections without metal grounding rings, these plastic disks/seals should never be removed and should always be installed!</li> <li>Grounding rings can be ordered separately as an accessory from Endress+Hauser . When ordering make sure that the grounding rings are compatible with the material used for the electrodes, as otherwise there is the danger that the electrodes could be destroyed by electrochemical corrosion!</li> <li>Grounding rings, including seals, are mounted inside the process connections. Therefore the installation length is not affected.</li> </ul>

Potential equalization via additional grounding ring



- Hexagonal-headed bolts of process connection
- 1 2 3 O-ring seals Plastic disk (spacer) or grounding ring
- 4 Sensor

# 2 3 Λ A0017293 Hexagonal-headed bolts of process connection 1 Integrated grounding electrodes 2 3 O-ring seal 4 Sensor Terminals • For device version without integrated overvoltage protection: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm<sup>2</sup> (20 to 14 AWG) • For device version with integrated overvoltage protection: screw terminals for wire cross-sections 0.2 to 2.5 mm<sup>2</sup> (24 to 14 AWG) **Cable entries** • Cable gland (not for Ex d): M20 $\times$ 1.5 with cable $\phi$ 6 to 12 mm (0.24 to 0.47 in) Thread for cable entry: - For non-Ex and Ex: NPT 1/2" - For non-Ex and Ex (not for CSA Ex d/XP): G 1/2" - For Ex d: M20 × 1.5 **Cable specification** Permitted temperature range ■ -40 °C (-40 °F) to +80 °C (+176 °F) ■ Minimum requirement: cable temperature range ≥ ambient temperature +20 K Signal cable Current output For 4-20 mA HART: Shielded cable recommended. Observe grounding concept of the plant. Pulse/frequency/switch output Standard installation cable is sufficient. FOUNDATION Fieldbus Twisted, shielded two-wire cable. For further information on planning and installing FOUNDATION Fieldbus networks see: Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S) FOUNDATION Fieldbus Guideline IEC 61158-2 (MBP)

# Potential equalization via grounding electrodes on process connection

# PROFIBUS PA

+

Twisted, shielded two-wire cable. Cable type A is recommended.

For further information on planning and installing PROFIBUS PA networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

# **Overvoltage** protection

The device can be ordered with integrated overvoltage protection for diverse approvals: *Order code for "Accessory mounted", option NA "Overvoltage protection"* 


Input voltage range	Values correspond to supply voltage specifications <sup>1)</sup>
Resistance per channel	$2 \cdot 0.5 \Omega$ max
DC sparkover voltage	400 to 700 V
Trip surge voltage	< 800 V
Capacitance at 1 MHz	< 1.5 pF
Nominal discharge current (8/20 µs)	10 kA
Temperature range	-40 to +85 °C (-40 to +185 °F)

1) The voltage is reduced by the amount of the internal resistance  $I_{\text{min}} \cdot R_i$ 

Depending on the temperature class, restrictions apply to the ambient temperature for device versions with overvoltage protection

# **Performance characteristics**

Reference operating conditions	<ul> <li>In accordance with DIN EN 29104</li> <li>Water, typically 15 to 45 °C (59 to 113 °F); 2 to 6 bar (29 to 87 psi)</li> <li>Data as indicated in the calibration protocol ±5 °C (±41 °F) and ±2 bar (±29 psi)</li> <li>Accuracy based on accredited calibration rigs traced to ISO 17025</li> <li>Medium temperature: +28 ± 2 °C (+82 ± 4 °F)</li> <li>Ambient temperature: +22 ± 2 °C (+72 ± 4 °F)</li> <li>Warm-up period: 30 min</li> </ul>		
	<ul> <li>Installation</li> <li>Inlet run &gt; 10 × DN</li> <li>Outlet run &gt; 5 × DN</li> <li>Sensor and transmitter grounded.</li> <li>The sensor is centered in the pipe.</li> </ul>		
	To calculate the measuring range, use the <i>Applicator</i> sizing tool $\rightarrow \cong 68$		
Maximum measured error	Error limits under reference operating conditions		
	o.r. = of reading		
	<b>Volume flow</b> ±0.5 % o.r. ± 2 mm/s (0.08 in/s)		
	Fluctuations in the supply voltage do not have any effect within the specified range.		



■ 7 Maximum measured error in % o.r.

# Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

Accuracy
----------

Pulse/frequency output

o.r. = of reading

Accuracy	Max. ±100 ppm o.r.
----------	--------------------

### Repeatability

o.r. = of reading

**Volume flow** Max. ±0.2 % o.r. ± 2 mm/s (0.08 in/s)

Influence of ambient temperature

# Current output

o.r. = of reading

Additional error, in relation to the span of 16 mA:

Temperature coefficient at zero point (4 mA)	0.02 %/10 K
Temperature coefficient with span (20 mA)	0.05 %/10 K

# Pulse/frequency output


o.r. = of reading

	Temperature coefficient	Max. ±100 ppm o.r.
--	-------------------------	--------------------

# Installation

No special measures such as supports are necessary. External forces are absorbed by the construction of the device.

# Mounting location



Preferably install the sensor in an ascending pipe, and ensure a sufficient distance to the next pipe elbow:  $h \ge 2 \times DN$ 

To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:


- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

# Installation in down pipes

Install a siphon with a vent valve downstream of the sensor in down pipes whose length  $h \ge 5$  m (16.4 ft). This precaution is to avoid low pressure and the consequent risk of damage to the measuring tube. This measure also prevents the system losing prime.



For information on the liner's resistance to partial vacuum




• 8 Installation in a down pipe

- 1 Vent valve
- 2 Pipe siphon
- h Length of down pipe

# Installation in partially filled pipes

A partially filled pipe with a gradient necessitates a drain-type configuration. The empty pipe detection (EPD) function offers additional protection by detecting empty or partially filled pipes.




# Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

An optimum orientation position helps avoid gas and air accumulations and deposits in the measuring tube.


The measuring device also offers the empty pipe detection function to detect partially filled measuring pipes in the event of outgassing fluids or variable process pressures.

Vertical



Optimum for self-emptying pipe systems and for use in conjunction with empty pipe detection.

# Horizontal




- 1 EPD electrode for empty pipe detection
- 2 Measuring electrodes for signal detection
- The measuring electrode plane must be horizontal. This prevents brief insulation of the two measuring electrodes by entrained air bubbles.
  - Empty pipe detection only works if the transmitter housing is pointing upwards as otherwise there is no guarantee that the empty pipe detection function will actually respond to a partially filled or empty measuring tube.

# Inlet and outlet runs

If possible, install the sensor upstream from fittings such as valves, T-pieces or elbows.

Observe the following inlet and outlet runs to comply with accuracy specifications:





Adapters

Suitable adapters to DIN EN 545 (double-flange reducers) can be used to install the sensor in largerdiameter pipes. The resultant increase in the rate of flow improves measuring accuracy with very slow-moving fluids.

The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders:

- Calculate the ratio of the diameters d/D.
- From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.





# Special mounting instructions

### **Display protection**

To ensure that the optional display protection can be easily opened, maintain the following minimum head clearance: 350 mm (13.8 in)


# Environment

### Ambient temperature range

Transmitter	-40 to +60 °C (-40 to +140 °F)
Local display	-20 to $+60$ °C ( $-4$ to $+140$ °F), the readability of the display may be impaired at temperatures outside the temperature range.
Sensor	-20 to +60 °C (-4 to +140 °F)
Liner	Do not exceed or fall below the permitted temperature range of the liner .

If operating outdoors:

- Install the measuring device in a shady location.
- Avoid direct sunlight, particularly in warm climatic regions.
- Avoid direct exposure to weather conditions.



# **Temperature tables**

The following interdependencies between the permitted ambient and fluid temperatures apply when operating the device in hazardous areas:

# NOTICE

# The ambient temperature changes for installations with overvoltage protection in conjunction with temperature classes T5 and T6.

The following applies for basic specification, position 1, 2 (approval) = BJ, B5, BH, IJ, I6, IH, C2, NF, N6, NH, NK, MJ:

 $\bullet \quad T_a = T_a - 2 K$ 

# SI units

Т <sub>а</sub> [°С]	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
40	80	95	130	150	150	150
55	_	95	130	150	150	150
60 <sup>1)</sup>	-	95	130	150	150	150

1) The following applies for Basic specification, Position 3 (Output) = A, B, E, G:  $P_i = 0.85 \text{ W}$ 

# US units

T <sub>a</sub> [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]
104	176	203	266	302	302	302
131	-	203	266	302	302	302
140 <sup>1)</sup>	_	203	266	302	302	302

1) The following applies for basic specification, position 3 (output) = A, B, E, G:  $P_i = 0.85 \text{ W}$ 

Storage temperature	The storage temperature corresponds to the operating temperature range of the measuring transmitter and the appropriate measuring sensors.
	<ul> <li>Protect the measuring device against direct sunlight during storage in order to avoid unacceptably high surface temperatures.</li> <li>Select a storage location where moisture cannot collect in the measuring device as fungus or bacteria infestation can damage the liner.</li> <li>If protection caps or protective covers are mounted these should never be removed before installing the measuring device.</li> </ul>
Degree of protection	Transmitter • As standard: IP66/67, type 4X enclosure • When housing is open: IP20, type 1 enclosure • Display module: IP20, type 1 enclosure
	<b>Sensor</b> IP66/67, type 4X enclosure
	<b>Connector</b> IP67, only in screwed situation
Shock resistance	As per IEC/EN 60068-2-31
Vibration resistance	Acceleration up to 2 g, according to IEC 60068-2-6
Mechanical load	<ul><li>Protect the transmitter housing against mechanical effects, such as shock or impact.</li><li>Never use the transmitter housing as a ladder or climbing aid.</li></ul>
Electromagnetic compatibility (EMC)	As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) For details, refer to the Declaration of Conformity.


# Process

Medium temperature range


–20 to +150  $^\circ C$  (–4 to +302  $^\circ F) for PFA$ 

Conductivity


ratings



 $T_A$ Ambient temperature  $T_{\rm F}$ Medium temperature 1 Hatched area: harsh environment only up to +130  $^\circ C$  (+266  $^\circ F)$  $\geq$  20 µS/cm for liquids in general **Pressure-temperature** The following pressure-temperature ratings refer to the entire device and not just the process connection. Process connections with O-ring seal, DN 2 to 25 (1/12 to 1") Process connection: weld-in nipple according to DIN EN ISO 1127, ODT/SMS, ISO 2037; coupling according to ISO 228 / DIN 2999, NPT




🛃 9 Process connection material: stainless steel, 1.4404 (F316L)




Process connection: flange according to EN 1092-1 (DIN 2501), adhesive sleeve


■ 10 Process connection material: stainless steel, 1.4404 (F316L)




■ 11 Process connection material: PVDF




■ 12 Process connection material: PVC-U






📧 13 Process connection material: stainless steel, 1.4404 (F316L)




■ 14 Process connection material: PVDF

Process connection: flange according to JIS B2220




■ 15 Process connection material: stainless steel, 1.4404 (F316L)



■ 16 Process connection material: PVDF


# Process connections with aseptic molded seal, DN 2 to 25 (1/12 to 1")

Process connection: weld-in nipple according to EN 10357 (DIN 11850), ASME BPE, ISO 2037; Clamp according to ISO 2852, DIN 32676, L14 AM7; coupling according to SC DIN 11851, DIN 11864-1, SMS 1145; flange according to DIN 11864-2



☑ 17 Process connection material: stainless steel, 1.4404 (F316L)

Pressure tightness	Liner: PFA									
	Nominal	diameter	Limit values for absolute pressure in [mbar] ([psi]) for fluid temperatures:							
	[mm]	[in]	+25 ℃ (+77 ℉)	+80 °C (+176 °F)	+100 ℃ (+212 ℉)	+130 °C (+266 °F)	+150 °C (+302 °F)			
	2 to 25	<sup>1</sup> / <sub>12</sub> to 1	0 (0)	0 (0)	0 (0)	0 (0)	0 (0)			
Flow limit	<ul> <li>The diameter of the pipe and the flow rate determine the nominal diameter of the sensor. The optimum velocity of flow is between 2 to 3 m/s (6.56 to 9.84 ft/s). Also match the velocity of flo (v) to the physical properties of the fluid:</li> <li>v &lt; 2 m/s (6.56 ft/s): for abrasive fluids</li> <li>v &gt; 2 m/s (6.56 ft/s): for fluids producing buildup</li> </ul>									
	A necessary increase in the flow velocity can be achieved by reducing the sensor nominal diameter.									
	For an overview of the measuring range full scale values, see the "Measuring range" section $\rightarrow \cong 5$									
Pressure loss	<ul> <li>No pressure loss occurs as of nominal diameter DN 8 (3/8") if the sensor is installed in a pipe with the same nominal diameter.</li> <li>Pressure losses for configurations incorporating adapters according to DIN EN 545 → ≅ 28</li> </ul>									



Never install the sensor on the pump suction side in order to avoid the risk of low pressure, and thus damage to the liner.


Furthermore, install pulse dampers if reciprocating, diaphragm or peristaltic pumps are used.


- For information on the liner's resistance to partial vacuum  $\rightarrow \square 34$
- For information on the shock resistance of the measuring system  $\rightarrow \implies 30$
- For information on the vibration resistance of the measuring system  $\rightarrow \cong 30$

Vibrations

In the event of very strong vibrations, the pipe and sensor must be supported and fixed.

• For information on the shock resistance of the measuring system  $\rightarrow \cong 30$ 






■ 18 Measures to avoid device vibrations (L > 10 m (33 ft))

# Mechanical construction

**Dimensions in SI units** 

# **Compact version**

Order code for "Housing", option C "GT20 dual compartment, aluminum coated"




DN	A	B 1)	С	D <sup>2)</sup>	E	F <sup>2)</sup>	G	H <sup>3)</sup>	J	K <sup>3)</sup>	L <sup>4)</sup>	Q	di
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
2	162	102	60	165	75	90	43	265	48	313	86	4 × M6	2.25
4	162	102	60	165	75	90	43	265	48	313	86	4 × M6	4.5
8	162	102	60	165	75	90	43	265	48	313	86	4 × M6	9
15	162	102	60	165	75	90	43	265	48	313	86	4 × M6	16
25	162	102	60	165	75	90	53	269	52	321	86	4 × M6	26

1)

For version without local display: values - 7 mm For version with overvoltage protection (OVP): values + 8 mm For version without local display: values - 10 mm Total length (L) depends on the process connections. 2) 3) 4)

# Sensor flange connection




If Front view without process connections

DN	А	В	С	D	Е	F	G	Н	К	L	М
[mm]											
2	62	41.6	34	9	24	42	43	8.5	6	4	M6
4	62	41.6	34	9	24	42	43	8.5	6	4	M6
8	62	41.6	34	9	24	42	43	8.5	6	4	M6
15	62	41.6	34	16	24	42	43	8.5	6	4	M6
25	72	50.2	44	26	29	55	56	8.5	6	4	M6

#### Flanges

Flanges with aseptic molded seal




 20 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier.

1.4404	Flange DIN 11864-2, aseptic female, Form A 1.4404 (316L) Order code for "Process connection", option DES									
DN [mm]	Suitable for pipe EN 10357 (DIN 11850) [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
2 to 8	13 × 1.5 (DN 10)	54	37	4 × Ø9	10	10	183			
15	19 × 1.5 (DN 15)	59	42	4 × Ø9	10	16	183			
25	29 × 1.5 (DN 25)	70	53	4 × Ø9	10	26	183			
Surface I	coughness: $R_a \le 0.8 \ \mu m$ , optional $\le 0.38 \ \mu m$									

Please note the internal diameters of the measuring tube and process connection (E) when cleaning with pigs.

# Flanges with O-ring seal



Flange according to EN 1092-1 (DIN 2501), Form B: PN 40         1.4404 (316L)         Order code for "Process connection", option D5S									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
2 to 8 <sup>1)</sup>	95	65	4ר14	16	17.3	198.4			
15	95	65	4ר14	16	17.3	198.4			

Flange according to EN 1092-1 (DIN 2501), Form B: PN 40 1.4404 (316L) Order code for "Process connection", option D5S									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
25	115	85	4ר14	18	28.5	198.4			
Surface roughness: $R_a \le 1.6 \ \mu m$									


1) DN 2 to 8 with DN 15 flanges as standard

Flange according to ASME B16.5: Class 150 1.4404 (316L) Order code for "Process connection", option A1S									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
2 to 8 <sup>1)</sup>	90	60.3	4 × Ø15.7	11.2	15.7	218			
15	90	60.3	4 × Ø15.7	11.2	15.7	218			
25	110	79.4	4 × Ø15.7	14.2	26.7	230			
Surface roughnes	ss: R <sub>a</sub> ≤ 1.6 µm								

1) DN 2 to 8 with DN 15 flanges as standard

Flange according to JIS B2220: 20K 1.4404 (316L) Order code for "Process connection", option N4S									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
2 to 8 <sup>1)</sup>	95	70	4 × Ø15	14	15	220			
15	95	70	4 × Ø15	14	15	220			
25	125	90	4ר19	16	25	220			
Surface roughnes	s: R <sub>a</sub> ≤ 1.6 µm								

1) DN 2 to 8 with DN 15 flanges as standard



#### Lap joint flange according to EN 1092-1 (DIN 2501): PN 16 PVDF Order code for "Process connection", option D3P

oraci coac joi	The course of th									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]			
2 to 8 <sup>1)</sup>	95	65	4 x Ø14	14.5	45	17.3	200			
15	95	65	4 x Ø14	14.5	45	17.3	200			
25	115	85	4 x Ø14	16.5	68	28.5	200			

Surface roughness:  $R_a \leq 1.6 \ \mu m$ 

The required grounding rings can be ordered as accessories (order code: DK5HR-\*\*\*\*).

DN 2 to 8 with DN 15 flanges as standard 1)

#### Lap joint flange with grounding electrode according to EN 1092-1 (DIN 2501): PN 16 PVDF

Order code for "Process connection", option D4P

-		•					
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]
2 to 8 <sup>1)</sup>	95	65	4 x Ø14	14.5	45	17.3	200
15	95	65	4 x Ø14	14.5	45	17.3	200
25	115	85	4 x Ø14	16.5	68	28.5	200
Surface rough	$P_{\text{R}} \leq 1.6$	ım					

Surface roughness:  $R_a \le 1.6 \ \mu m$ Grounding rings are not necessary.

DN 2 to 8 with DN 15 flanges as standard 1)

Lap joint flange according to ASME B16.5: Class 150 PVDF Order code for "Process connection", option A1P									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]		
2 to 8 <sup>1)</sup>	90	60.3	4 × Ø 15.7	15	35.1	15.7	200		
15	90	60.3	4 × Ø 15.7	15	35.1	15.7	200		
25	110	79.4	4 × Ø 15.7	16	50.8	26.7	200		

Surface roughness:  $R_a \le 1.6 \ \mu m$ 

The required grounding rings can be ordered as accessories (order code: DK5HR-\*\*\*\*).

DN 2 to 8 with DN 15 flanges as standard 1)

Order code for "Process connection", option A4P								
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm	
2 to 8 <sup>1)</sup>	90	60.3	4 × Ø 15.7	15	35.1	15.7	200	
15	90	60.3	4 × Ø 15.7	15	35.1	15.7	200	
25	110	79.4	4 × Ø 15.7	16	50.8	26.7	200	

Grounding rings are not necessary.

DN 2 to 8 with DN 15 flanges as standard 1)

#### Endress+Hauser

Lap joint flange according to JIS B2220: 10K PVDF Order code for "Process connection", option N3P									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]		
2 to 8 <sup>1)</sup>	95	70	4 × Ø 15.7	15	35.1	15	200		
15	95	70	4 × Ø 15.7	15	35.1	15	200		
25	125	90	4 × Ø 15.7	16	50.8	19	200		
Surface rough	- ness: R. < 1.6	um	1	1	1	1	1		

The required grounding rings can be ordered as accessories (order code: DK5HR-\*\*\*\*).

1) DN 2 to 8 with DN 15 flanges as standard

# Lap joint flange with grounding electrode according to JIS B2220: 10K PVDF

Order code for "Process connection", option N4P


· · · · · · · · · · · · · · · · · · ·		, . <u>r</u>					
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]
2 to 8 <sup>1)</sup>	95	70	4 × Ø 15.7	15	35.1	15	200
15	95	70	4 × Ø 15.7	15	35.1	15	200
25	125	90	4 × Ø 15.7	16	50.8	19	200
Surface rough	u	•					

Grounding rings are not necessary.

1) DN 2 to 8 with DN 15 flanges as standard

# Welding nipple

Welding nipple with aseptic molded seal



Welding nipple according to EN 10357 (DIN 11850) 1.4404 (316L) Order code for "Process connection", option DAS									
DN [mm]	Suitable for pipe EN 10357 (DIN 11850) [mm]	A [mm]	B [mm]	L [mm]					
2 to 8	13 × 1.5	13	10	132.6					
15	19 × 1.5	19	16	132.6					
25	29 × 1.5	29	26	132.6					
	hess: $R_a \le 0.8 \ \mu\text{m}$ , optional $\le 0.38 \ \mu\text{m}$ e internal diameters of the measuring tube and proc	ess connection	(B) when cleani	ng with pigs.					

Welding nipple according to ISO 2037 1.4404 (316L) Order code for "Process connection", option IAS					
DN [mm]	Suitable for pipe ISO 2037 [mm]	A [mm]	B [mm]	L [mm]	
2 to 8	12.7 × 1.65	12	10	118.2	
15	19.05 × 1.65	18	16	118.2	
25	25.4 × 1.60	25	22.6	118.2	

Surface roughness:  $R_a \leq 0.8~\mu m,$  optional  $\leq 0.38~\mu m$ 


Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

#### Welding nipple according to ASME BPE 1.4404 (316L) Order code for "Process connection", option AAS DN Suitable for pipe ASME BPE Α В L [mm] [mm] [mm] [mm] [mm] 2 to 8 12.7 × 1.65 12.7 9 118.2 15 19.1 × 1.65 19.1 118.2 16 25 25.4 $25.4 \times 1.65$ 22.6 118.2

Surface roughness:  $R_a \leq 0.8~\mu m,$  optional  $\leq 0.38~\mu m$ 

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

Welding nipple with O-ring seal



Welding nipple according to ODT/SMS 1.4404 (316L) Order code for "Process connection", option A2S				
DN [mm]	Suitable for pipe ODT/SMS [mm]	A [mm]	B [mm]	L [mm]
2 to 8	13.5 × 2.30	13.5	9	126.6
15	21.3 × 2.65	21.3	16	126.6
25	33.7 × 3.25	33.7	27.2	126.6
Surface rough	Surface roughness: $R_a \le 1.6 \ \mu m$			


Welding nipple according to DIN EN ISO 1127         1.4404 (316L)         Order code for "Process connection", option D1S					
DN [mm]	Suitable for pipe DIN EN ISO 1127 [mm]	A [mm]	B [mm]	L [mm]	
2 to 8	13.5 × 1.6	13.5	10.3	126.6	
15	21.3 × 1.6	21.3	18.1	126.6	
25	33.7 × 2.0	33.7	29.7	126.6	
Surface roug	Surface roughness: $R_a \le 1.6 \ \mu m$				

#### Welding nipple according to ISO 2037 1.4404 (316L) Order code for "Process connection", option IIS DN Suitable for pipe ISO 2037 Α В L [mm] [mm] [mm] [mm] [mm] 2 to 8 13.5 × 2.3 13.5 9 126.6 15 21.3 × 2.65 21.3 16 126.6 25 33.7 × 3.25 33.7 27.2 126.6

Surface roughness:  $R_a \leq 1.6 \ \mu m$ 

#### **Clamp connections**

Clamp connections with aseptic molded seal



Clamp according to DIN 32676 1.4404 (316L) Order code for "Process connection", option DBS				
DN [mm]	Suitable for pipe EN 10357 (DIN 11850) [mm]	A [mm]	B [mm]	L [mm]
2 to 8	14 × 2 (DN 10)	34	10	168
15	20 × 2 (DN 15)	34	16	168
25	30 × 2 (DN 25)	50.5	26	175

Surface roughness:  $R_a \leq 0.8~\mu m$  , optional  $\leq 0.38~\mu m$ 

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

Tri-Clamp
1.4404 (316L)

Order code for "Process connection", option FAS

DN [mm]	Suitable for pipe as per ASME BPE [mm]	A [mm]	B [mm]	L [mm]
2 to 8	12.7 × 1.65	25	9.4	143
15	19.1 × 1.65	25	15.8	143
25	25.4 × 1.65	50.4	22.1	143

Surface roughness:  $R_a \leq 0.8~\mu m,$  optional  $\leq 0.38~\mu m$ 

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.


Clamp according to ISO 2852, Fig. 2 1.4404 (316L) Order code for "Process connection", option IBS				
DN [mm]	Suitable for pipe ISO 2037 [mm]	A [mm]	B [mm]	L [mm]
25	24.5 × 1.65	50.5	22.6	174.6

Surface roughness:  $R_a \leq 0.8~\mu m,$  optional  $\leq 0.38~\mu m$ 

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

### Cable glands

Threaded adapter with aseptic molded seal



Coupling SC DIN 11851, threaded adapter 1.4404 (316L) Order code for "Process connection", option DCS				
DN [mm]	Suitable for pipe EN 10357 (DIN 11850) [mm]	A [mm/in]	B [mm]	L [mm]
2 to 8	12 × 1 (DN 10)	Rd 28 × $\frac{1}{8}$	10	174
15	18 × 1.5 (ODT ¾")	Rd 34 × $\frac{1}{8}$	16	174
25	28 × 1 or 28×1.5	Rd 52 × ¼	26	190

Surface roughness:  $R_a \leq 0.8~\mu m,$  optional  $\leq 0.38~\mu m$ 

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.


Coupling DIN 11864-1, aseptic threaded hygienic connection, Form A 1.4404 (316L) Order code for "Process connection", option DDS						
DN [mm]	Suitable for pipe EN 10357 (DIN 11850) [mm]	A [mm/in]	B [mm]	L [mm]		
2 to 8	Pipe 13 × 1.5 (DN 10)	Rd 28 × 1/8	10	170		
15	Pipe 19 × 1.5	Rd 34 × 1/8	16	170		
25	25         Pipe 29 × 1.5         Rd 52 × <sup>1</sup> / <sub>6</sub> 26         184					
Surface rough	$P_{\rm max} = R < 0.8  \mu m$ optional < 0.38 $\mu m$					

Surface roughness:  $R_a \le 0.8 \ \mu m$ , optional  $\le 0.38 \ \mu m$ Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

Coupling SMS 1145, threaded adapter 1.4404 (316L) Order code for "Process connection", option SAS					
DN [mm]	Suitable for pipe ODT [mm]	DN SMS 1145 [mm]	A [mm/in]	B [mm]	L [mm]
25	1	25	Rd40 × 1/6	22.6	147.6
Surface roughness: $R_a \le 0.8 \ \mu m$ , optional $\le 0.38 \ \mu m$					

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

Threaded adapter with O-ring seal




External thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I2S					
DN [mm]	A [mm/in]	B [mm]	L [mm]		
2 to 8	R 10.1 × 3/8	10	166		
15	R 13.2 × ½	16	166		
25	R 16.5 × 1	25	170		
Surface roughness: $R_a \le$	Surface roughness: $R_a \le 1.6 \ \mu m$				

Internal thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I3S				
DN [mm]	A [mm/in]	B [mm]	L [mm]	
2 to 8	Rp 13 × 3/8	9	176	
15	Rp 14 × 1⁄2	16	176	

Internal thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I3S									
DN [mm]	A [mm/in]	B [mm]	L [mm]						
25	Rp 17 × 1	27.2	188						
Surface roughness: $R_a \le 1.6 \ \mu m$									

# Hose adapter


Hose adapter with O-ring seal



Hose adapter 1.4404 (316L) Order code for "Process connection", options O1S, O2S, O3S											
DN [mm]	Suitable for internal diameter [mm]	A [mm]	L [mm]								
2 to 8	13	10	184								
15	16	12.6	184								
25	19	16	184								
Surface roughn	ess: R <sub>a</sub> ≤ 1.6 μm	1									

# Adhesive sleeves

Adhesive sleeves with O-ring seal




Adhesive sleeve PVC Order code for "Process connection", options O1V, O2V										
DN [mm]	Suitable for pipe [mm] / [in]	A [mm]	B [mm]	L [mm]						
2 to 8	20 × 2 (DIN 8062)	27	20.2	163						
15	1/2	27.3	21.5	163						
25	20 × 2 (DIN 8062)	27	20.2	142						
Surface roughness	: R <sub>a</sub> ≤ 1.6 µm									

The required grounding rings can be ordered as accessories (order code: DK5HR-\*\*\*\*).

# Mountings sets


Wall mounting kit



А	В	B C ØD		Е	F
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
137	110	120	7	125	88

# Accessories


Clamp connections with aseptic molded seal available for order



1.4404 (3	Tri-Clamp 1.4404 (316L) Order code: DKH**-HF**											
DN [mm]	Suitable for pipe in accordance with ASME BPE (reduction) [mm]	A [mm]	B [mm]	L [mm]								
15	Pipe ODT 1	50.4	22.1	143								
Surface ro	ıghness: R <sub>a</sub> ≤ 0.8 μm, optional ≤ 0.38 μm											

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

# Threaded glands with O-ring seal available for order






External thread 1.4404 (316L) Order code: DKH**-GD**											
DN [mm]	Suitable for NPT internal thread [in]	A [mm/in]	B [mm]	L [mm]							
2 to 8	NPT 3/8	R 15.5 × 3/8	10	186							
15	NPT ½	R 20 × ½	16	186							
25	25 NPT 1 R 25 × 1 25 196										

Surface roughness:  $R_a \le 1.6 \ \mu m$ 

Internal thread 1.4404 (316L) Order code: DKH**-GC**											
DN [mm]	Suitable for NPT external thread [in]	A [mm/in]	B [mm]	L [mm]							
2 to 8	NPT 3/8	R 13 × 3/8	8.9	176							
15	NPT ½	R 14 × ½	16	176							
25	NPT 1	R 17 × 1	27.2	188							
Surface rou	ghness: $R_a \le 1.6 \ \mu m$	1									

# Grounding rings




For lap joint flange made of PVDF and PVC adhesive sleeve 1.4435 (316L), Alloy C22, tantalum Order code: DK5HR-****										
DN di B C D E F							G	Н	J	
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	
2 to 8	9	22	17.6	33.9	0.5	3.5	1.9	3.4	4.5	
15	16	29	24.6	33.9	0.5	3.5	1.9	3.4	4.5	
25	26	39	34.6	43.9	0.5	3.5	1.9	3.4	4.5	

### Dimensions in US units

## Compact version

# Order code for "Housing", option C "GT20 dual compartment, aluminum coated"



DN	A	B 1)	С	D <sup>2)</sup>	E	F	G	H <sup>3)</sup>	J	К	L <sup>4)</sup>	Q	di
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[mm]	[in]
1/12	6.38	4.02	2.36	6.50	2.95	3.54	1.69	10.39	1.88	12.27	3.39	4 × M6	0.09
5/32	6.38	4.02	2.36	6.50	2.95	3.54	1.69	10.39	1.88	12.27	3.39	4 × M6	0.18
5/16	6.38	4.02	2.36	6.50	2.95	3.54	1.69	10.39	1.88	12.27	3.39	4 × M6	0.35


DN	A	B 1)	С	D <sup>2)</sup>	E	F	G	H <sup>3)</sup>	J	К	L <sup>4)</sup>	Q	di
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[mm]	[in]
1/2	6.38	4.02	2.36	6.50	2.95	3.54	1.69	10.39	1.88	12.27	3.39	4 × M6	0.63
1	6.38	4.02	2.36	6.50	2.95	3.54	2.07	10.55	2.04	12.59	3.39	4 × M6	1.02

1) 2) 3) 4)

For version without local display: values - 0.28 in For version with overvoltage protection (OVP): values + 0.31 in For version without local display: values - 0.39 in

Total length (L) depends on the process connections.

### Sensor flange connection




	_ · · · · · · · · · · · · · · · · · · ·	
🖸 21	Front view without process connectio	ns

DN	A	В	С	D	E	F	G	Н	К	L	М
[in]	[mm]										
1/12	2.44	1.64	1.34	0.35	0.94	1.65	1.69	0.33	0.24	0.16	M6
5/32	2.44	1.64	1.34	0.35	0.94	1.65	1.69	0.33	0.24	0.16	M6
5/16	2.44	1.64	1.34	0.35	0.94	1.65	1.69	0.33	0.24	0.16	M6
1/2	2.44	1.64	1.34	0.63	0.94	1.65	1.69	0.33	0.24	0.16	M6
1	2.83	1.98	1.73	0.89	1.14	2.17	2.20	0.33	0.24	0.16	M6


# Flanges

Flanges with O-ring seal



Flange according to ASME B16.5: Class 150         1.4404 (316L)         Order code for "Process connection", option A1S							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]	
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub> <sup>1)</sup>	3.50	2.38	4 × Ø 0.62	0.44	0.62	8.59	
1/2	3.50	2.38	4 × Ø 0.62	0.44	0.63	8.59	
1	4.25	3.12	4 × Ø 0.62	0.56	1.05	9.05	
Surface roughness: R <sub>a</sub> :	≤ 63 µin						

1) DN  $\frac{1}{12}$  to  $\frac{3}{8}$  with DN  $\frac{1}{2}$ " flanges as standard



Lap joint flange according to ASME B16.5: Class 150 PVDF Order code for "Process connection", option A1P							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub> <sup>1)</sup>	3.74	2.36	4 × Ø 0.62	0.59	1.38	0.63	7.87
1/2	3.74	2.36	4 × Ø 0.62	0.59	1.38	0.63	7.87
Surface roughness The required grou	u I		ed as accessories (orc	ler code: DK	5HR-****).		


1) DN  $\frac{1}{12}$  to  $\frac{3}{8}$  with DN  $\frac{1}{2}$ " flanges as standard

Lap joint flange according to ASME B16.5: Class 150 PVDF Order code for "Process connection", option A4P							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub> <sup>1)</sup>	3.74	2.36	4 × Ø 0.62	0.59	1.38	0.63	7.87
1/2	3.74	2.36	4 × Ø 0.62	0.59	1.38	0.63	7.87

1) DN  $\frac{1}{12}$  to  $\frac{3}{8}$  with DN  $\frac{1}{2}$ " flanges as standard

# Welding nipple

Welding nipple with aseptic molded seal



Welding nipple according to ISO 2037 1.4404 (316L) Order code for "Process connection", option IAS							
DN [in]	Suitable for pipe ISO 2037 [in]	A [in]	B [in]	L [in]			
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	0.50 × 0.06	0.47	0.39	4.65			
1/2	0.75 × 0.06	0.71	0.63	4.65			
1	1.00 × 0.06	0.98	0.89	4.65			

Surface roughness:  $R_a \leq 31.5~\mu in,$  optional  $\leq 15~\mu in$ 


Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

Welding nipple according to ASME BPE 1.4404 (316L) Order code for "Process connection", option AAS						
DN [in]	Suitable for pipe ASME BPE [in]	A [in]	B [in]	L [in]		
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	0.50 × 0.06	0.50	0.35	4.65		
1/2	0.75 × 0.06	0.75	0.63	4.65		
1	1.00 × 0.06	1.00	0.89	4.65		

Surface roughness:  $R_a \leq 31.5~\mu in,$  optional  $\leq 15~\mu in$ 

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.


Welding nipple with O-ring seal



Welding nipple according to ODT/SMS 1.4404 (316L) Order code for "Process connection", option A2S					
DN [in]	Suitable for pipe ODT/SMS [in]	A [in]	B [in]	L [in]	
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	0.53 × 0.09	0.53	0.35	4.99	
1/2	0.84 × 0.10	0.84	0.63	4.99	
Surface roughness	s: R <sub>a</sub> ≤ 63 μin				

# **Clamp connections**

Clamp connections with aseptic molded seal



Tri-Clamp 1.4404 (316L) Order code for "Pro	cess connection", option <b>FAS</b>			
DN [in]	Suitable for pipe as per ASME BPE [in]	A [in]	B [in]	L [in]
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	1/2	1	0.37	5.63
1/2	3/4	25	0.62	5.63
1	1	2	0.87	5.63
Surface roughness	$R_{\rm e} < 31.5$ µin optional < 15 µin			


Surface roughness:  $R_a \le 31.5 \ \mu$ in, optional  $\le 15 \ \mu$ in Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

Clamp according to ISO 2852, Fig. 2 1.4404 (316L) Order code for "Process connection", option IBS							
DN [in]	Suitable for pipe ISO 2037 [in]	DN Clamp ISO 2852 [in]	A [in]	B [in]	L [in]		
1	0.96 × 0.06	1	2.00	0.89	6.87		
Surface rou	$ahness: R_s \le 31.5 \ \muin. \ optional \le 15$	uin					

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

#### Cable glands

Threaded adapter with aseptic molded seal



1.4404 (31	Coupling SC DIN 11851, threaded adapter 1.4404 (316L) Order code for "Process connection", option DCS						
DN [in]	Suitable for pipe EN 10357 (DIN 11850) [in]	A [in]	B [in]	L [in]			
1/2	Pipe ODT ¾	Rd0.05 × 0.13	0.63	6.85			

Surface roughness:  $R_a \le 31.5 \ \mu$ in, optional  $\le 15 \ \mu$ in


Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

Coupling SMS 1145, threaded adapter 1.4404 (316L) Order code for "Process connection", option SAS							
DN [in]	Suitable for pipe ODT [in]	DN SMS 1145 [in]	A [in]	B [in]	L [in]		
1	1	1	Rd1.57 × 0.17	0.89	5.81		

Surface roughness:  $R_a \le 31.5 \mu in$ , optional  $\le 15 \mu in$ 

Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.

# Threaded adapter with O-ring seal




External thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I2S							
DN [in]	Suitable for internal thread ISO 228 / DIN 2999 [in]	A [in]	B [in]	L [in]			
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	R 3/8	Rd 0.40 × 3/8	0.39	6.53			
1/2	R 1/2	Rd 0.52 × ½	0.63	6.53			
1	R 1	Rd 0.66 × 1	0.98	6.69			
Surface rou	ghness: R <sub>a</sub> ≤ 63 µin						

Internal thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I3S						
DN [in]	Suitable for external thread ISO 228 / DIN 2999 [in]	A [in]	B [in]	L [in]		
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	Rp 3/8	Rd 0.51 × 3/8	0.35	6.93		
1/2	Rp ½	Rd 0.55 × ½	0.63	6.93		
1	Rp 1	Rd 0.67 × 1	1.07	7.41		
Surface rou	ghness: $R_a \le 63 \mu in$	·				

# Adhesive sleeves


Adhesive sleeves with O-ring seal



<b>PVC</b> Order code for "Proce	ss connection", options <b>01V, 02V</b>			
DN [in]	Suitable for pipe [in]	A [in]	B [in]	L [in]
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	1/2	1.07	0.85	6.43

# Mountings sets


Wall mounting kit




А	В	С	ØD	Е	F
[in]	[in]	[in]	[in]	[in]	[in]
5.39	4.33	4.72	0.28	4.92	3.46

#### Accessories


Clamp connections with aseptic molded seal available for order





Tri-Clamp 1.4404 (316L) Order code: DKH**-HF**						
DN [in]	Suitable for pipe in accordance with ASME BPE (reduction) [in]	A [in]	B [in]	L [in]		
1/2	½         Pipe ODT 1         2         0.87         5.63					
Surface roughness: $R_a \le 31.5 \ \mu$ in, optional $\le 15 \ \mu$ in Please note the internal diameters of the measuring tube and process connection (B) when cleaning with pigs.						


Threaded glands with O-ring seal available for order



External three 1.4404 (316L Order code: D	)			
DN [in]	Suitable for NPT internal thread [in]	A [in]	B [in]	L [in]
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	NPT 3/8	R 0.61 × 3/8	0.39	7.39
1/2	NPT ½	R 0.79 × ½	0.63	7.39
1	NPT 1	R 1 × 1	1.00	7.73
Surface rough	ness: R <sub>a</sub> ≤ 63 µin			

Internal thread 1.4404 (316L) Order code: DKH**-GC**					
DN [in]	Suitable for NPT external thread [in]	A [in]	B [in]	L [in]	
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	NPT 3/8	R 0.51 × 3/8	0.35	6.93	
1/2	NPT ½	R 0.55 × ½	0.63	6.93	
1	NPT 1	R 0.67 × 1	1.07	7.41	
Surface rough	ness: $R_a \le 63 \mu in$				

#### Grounding rings



#### For lap joint flange made of PVDF and PVC adhesive sleeve 1.4435 (316L), Alloy C22, tantalum Order code: DK5HR-\*\*\*\*

Order code: DK5HK	-								
DN	di	В	С	D	E	F	G	Н	J
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
<sup>1</sup> / <sub>12</sub> to <sup>3</sup> / <sub>8</sub>	0.35	0.87	0.69	1.33	0.02	0.14	0.07	0.13	0.18
1/2	0.63	1.14	0.97	1.33	0.02	0.14	0.07	0.13	0.18
1	0.89	1.44	1.23	1.73	0.02	0.14	0.07	0.13	0.18

### Weight

All values (weight exclusive of packaging material) refer to devices for standard pressure ratings. Different values due to different transmitter versions:

#### **Compact version**

- Including the transmitter (1.9 kg (4.2 lbs))
- Weight specifications apply to standard pressure ratings and without packaging material.

Nominal diameter		Weight		
[mm]	[in]	[kg]	[lbs]	
2	1/12	3.7	8.2	
4	5/32	3.7	8.2	
8	5/16	3.8	8.4	
15	1/2	3.9	8.6	
25	1	4.0	8.8	

Measuring tube s	specification
------------------	---------------

Nominal	diameter	Pressure rating <sup>1)</sup>	Process connection	internal diameter
		EN (DIN)	PF	Ā
[mm]	[in]	[bar]	[mm]	[in]
2	1/12	PN 16/40	2.25	0.09
4	5/32	PN 16/40	4.5	0.18
8	5/16	PN 16/40	9.0	0.35
15	1/2	PN 16/40	16.0	0.63

Nominal	diameter	Pressure rating <sup>1)</sup> EN (DIN)		
[mm]	[in]	[bar]	[mm]	[in]
-	1	PN 16/40	22.6	0.89
25	-	PN 16/40	26.0	1.02


1) Depending on process connection and seals used

## Materials

#### Transmitter housing

- Order code for "Housing", option C "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
- Window material: glass

#### Cable entries/cable glands



#### 23 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland M20 × 1.5
- 3 Adapter for cable entry with internal thread G  $\frac{1}{2}$  or NPT  $\frac{1}{2}$
- 4 Device plug connectors

### Order code for "Housing", option C "GT20 dual compartment, aluminum coated"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	<ul><li>Non-Ex</li><li>Ex ia</li><li>Ex ic</li></ul>	Plastic
	Adapter for cable entry with internal thread G ½"	Nickel-plated brass
Adapter for cable entry with internal thread NPT ½"	For non-Ex and Ex (except for CSA Ex d/XP)	Nickel-plated brass
Thread NPT ½" via adapter	For non-Ex and Ex	

#### Device plug

Electrical connection	Material
Plug M12x1	<ul> <li>Socket: stainless steel, 1.4401/316</li> <li>Contact housing: plastic, PUR, black</li> <li>Contacts: metal, CuZn, gold-plated</li> <li>Threaded connection seal: NBR</li> </ul>

#### Sensor housing

Stainless steel 1.4301 (304)

#### Measuring tubes

Stainless steel 1.4301 (304)

#### Liner

PFA (USP Class VI, FDA 21 CFR 177.1550, 3A)

#### **Process connections**

- Stainless steel, 1.4404 (F316L)
- PVDF
- PVC adhesive sleeve

#### Electrodes

- Standard: 1.4435 (316L)
- Optional: Alloy C22, tantalum, platinum

#### Seals

- O-ring seal: EPDM, FKM, Kalrez
- Aseptic molded seal: EPDM <sup>1)</sup>, FKM, silicone <sup>1)</sup>

## Accessories

#### Protective cover

Stainless steel, 1.4404 (316L)

#### Grounding rings

Standard: 1.4435 (316L)Optional: Alloy C22, tantalum

#### Wall mounting kit

Stainless steel 1.4301 (304)

Fitted electrodes	Measuring electrodes and empty pipe detection electrodes (only DN 25 (1")): 1.4435 (316L), Alloy C22, platinum, tantalum	
Process connections	With O-ring seal: • Welding nipple (DIN EN ISO 1127, ODT/SMS, ISO 2037) • Flange (EN (DIN), ASME, JIS) • Flange from PVDF (EN (DIN), ASME, JIS) • External thread • Internal thread • Hose connection • PVC adhesive sleeve	
	With aseptic molded seal: • Welding nipple (EN 10357 (DIN 11850), ODT/SMS, ISO 2037) • Clamp (ISO 2852, DIN 32676, L14 AM7) • Coupling (DIN 11851, DIN 11864-1, ISO 2853, SMS 1145) • Flange DIN 11864-2	
	For information on the different materials used in the process connections $\rightarrow \square 59$	
Surface roughness	Stainless steel electrodes, 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); platinum; tantalu $\leq$ 0.3 to 0.5 µm (11.8 to 19.7 µin) (All data relate to parts in contact with fluid)	

<sup>1)</sup> USP Class VI, FDA 21 CFR 177.2600, 3A

Liner with PFA:  $\leq 0.4 \ \mu m \ (15.7 \ \mu in)$  (All data relate to parts in contact with fluid)

Stainless steel process connections:

- With O-ring seal:  $\leq 1.6 \ \mu m \ (63 \ \mu in)$
- With aseptic seal: ≤ 0.8 µm (31.5 µin) (All data relate to parts in contact with fluid)

# Operability

Operating concept	Operator-oriented menu structure for user-specific tasks <ul> <li>Commissioning</li> <li>Operation</li> <li>Diagnostics</li> <li>Expert level</li> </ul> <li>Quick and safe commissioning <ul> <li>Guided menus ("Make-it-run" wizards) for applications</li> <li>Menu quidance with brief explanations of the individual parameter functions</li> </ul> </li>			
	<ul> <li>Reliable operation</li> <li>Operation in the following languages: <ul> <li>Via local display:</li> <li>English, German, French, Spanish, Italian, Dut Chinese, Japanese, Bahasa (Indonesian), Vietr</li> <li>Via "FieldCare" operating tool:</li> <li>English, German, French, Spanish, Italian, Chi</li> </ul> </li> <li>Uniform operating philosophy applied to device</li> <li>If replacing the electronic module, transfer the c (integrated HistoROM) which contains the proce logbook. No need to reconfigure.</li> </ul> Efficient diagnostics increase measurement ava <ul> <li>Troubleshooting measures can be called up via t</li> <li>Diverse simulation options, logbook for events the</li> </ul>	nese, Japanese and operating tools evice configuration via the integrated memory ess and measuring device data and the event <b>ilability</b> he device and in the operating tools		
Local operation	Via display module			
	Order code for "Display; Operation", option <b>C</b> "SD02"	Order code for "Display; Operation", option <b>E</b> "SD03"		
	1	1		
	A01554	A0015546		

# **Display elements**

- 4-line display
- With order code for "Display; operation", option E:
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F)
   The readability of the display may be impaired at temperatures outside the temperature range.


#### **Operating elements**

- With order code for "Display; operation", option **C**:
- Local operation with 3 push buttons: 🕑, 🕑, 🕥
- With order code for "Display; operation", option **E**:
- External operation via touch control; 3 optical keys: 💮, 💿, 🖲
- Operating elements also accessible in various hazardous areas

#### Additional functionality

- Data backup function
- The device configuration can be saved in the display module.
- Data comparison function The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function
   The transmitter configuration can be transmitted to another device using the display module.

#### Via remote display and operating module FHX50




#### 24 Operating options via FHX50

- *1 Housing of remote display and operating module FHX50*
- 2 SD02 display and operating module, push buttons: cover must be opened for operation
- 3 SD03 display and operating module, optical buttons: operation possible through cover glass

#### **Remote operation**

#### Via HART protocol

#### This communication interface is available in device versions with a HART output.




#### 25 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 VIATOR Bluetooth modem with connecting cable
- 9 Transmitter

#### Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.




🖻 26 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2
- Segment coupler PROFIBUS DP/PA Computer with PROFIBUS network card 3
- PROFIBUS DP network 4
- 5 PROFIBUS PA network
- Measuring device 6
- 7 T-box

#### Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




27 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- 3 Industry network
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device

#### Service interface

#### Via service interface (CDI)



1 Service interface (CDI = Endress+Hauser Common Data Interface) of the measuring device

- Commubox FXA291
   Computer with "Field
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

# Certificates and approvals

CE mark	The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied.	
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.	
<b>C-Tick symbol</b> The measuring system meets the EMC requirements of the "Australian Communication Authority (ACMA)".		
Ex approval	The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.	
	The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.	
	ATEX, IECEx	

Currently, the following versions for use in hazardous areas are available:

#### Ex d

Category	Type of protection
II2G / Zone 1	Ex d[ia] IIC T6-T1 Gb
II2D / Zone 21	Ex tb IIIC T** Db

### Ex ia

Category	Type of protection
II2G / Zone 1	Ex ia IIC T6-T1 Gb
III2D / Zone 21	Ex tb IIIC T** Db

#### Ex nA

Category	Type of protection
II3G / Zone 2	Ex nA IIC T6-T1 Gc

#### Ex ic

Category	Type of protection
II3G / Zone 2	Ex ic IIC T6-T1 Gc

### cCSAus

Currently, the following versions for use in hazardous areas are available:

#### XP

Category	Type of protection
Class I/II/III Division 1 Groups ABCDEFG	XP (Ex d Flameproof version)

# IS

Category	Type of protection
Class I/II/III Division 1 Groups ABCDEFG	IS (Ex i Intrinsically safe version), Entity parameter $^{1)}$

1) Entity and NIFW parameter in accordance with Control Drawings

	NI		
	Category	Type of protection	
	Class I Division 2 Groups ABCD	NI (Non-incendive version), NIFW parameter $^{1)}$	
	1) Entity and NIFW parameter in accordance with Control Drawings		
Sanitary compatibility	<ul> <li>3A approval and EHEDG-certified</li> <li>Seals → in conformity with FDA (apart from Kalrez seals)</li> </ul>		
Functional safety	The measuring device can be used for flow mor (single-channel architecture) and SIL 3 (multicl and is independently evaluated and certified by	hannel architecture with homogeneous redundancy)	
	The following types of monitoring in safety equ Volume flow	lipment are possible:	
	Functional Safety Manual with informatio	n on the SIL device $\rightarrow \square 70$	
HART certification	HART interface		
	The measuring device is certified and registered by the HCF (HART Communication Founda The measuring system meets all the requirements of the following specifications: • Certified according to HART 7 • The device can also be operated with certified devices of other manufacturers (interopera		
FOUNDATION Fieldbus	FOUNDATION Fieldbus interface		
certification	d by the Fieldbus FOUNDATION. The measuring ving specifications: ieldbus H1 on 6.1.1 (certificate available on request) d devices of other manufacturers (interoperability)		
Certification PROFIBUS	PROFIBUS interface		
	measuring system meets all the requirements o Certified in accordance with PROFIBUS PA Pr		
	-		
Other standards and guidelines	<ul> <li>IEC/EN 61326</li> </ul>	for measurement, control and laboratory use	
	<ul> <li>Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).</li> <li>ANSI/ISA-61010-1 (82.02.01): 2004 Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1 General Requirements</li> <li>CAN/CSA-C22.2 No. 61010-1-04</li> </ul>		
	Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1 General Requirements • NAMUR NE 21		
	<ul><li>Electromagnetic compatibility (EMC) of indus</li><li>NAMUR NE 32</li><li>Data retention in the event of a power failure</li></ul>	strial process and laboratory control equipment e in field and control instruments with	
	analog output signal.	eakdown information of digital transmitters with	
	<ul> <li>NAMUR NE 53 Software of field devices and signal-processir</li> </ul>	ng devices with digital electronics	

- NAMUR NE 105
- Specifications for integrating fieldbus devices in engineering tools for field devices

  NAMUR NE 107
- Self-monitoring and diagnosis of field devices
- NAMUR NE 131
   Requirements for field devices for standard applications

# **Ordering information**

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select your country → Products → Select measuring technology, software or components → Select the product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product opens.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

#### Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

# **Application packages**

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Diagnostics functions	Package	Description
	HistoROM extended function	Comprises extended functions concerning the event log and the activation of the measured value memory.
		Event log: Memory volume is extended from 20 message entries (basic version) to up to 100 entries.
		<ul> <li>Data logging (line recorder):</li> <li>Memory capacity for up to 1000 measured values is activated.</li> <li>250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user.</li> <li>Data logging is visualized via the local display or FieldCare.</li> </ul>

Heartbeat Technology	Package	Description
	Heartbeat Verification	<ul> <li>Heartbeat Verification:</li> <li>Makes it possible to check the device functionality on demand when the device is installed, without having to interrupt the process.</li> <li>Access via local operation or other operating interfaces, such as FieldCare for instance.</li> <li>Documentation of device functionality within the framework of manufacturer specifications, for proof testing for instance.</li> <li>End-to-end, traceable documentation of the verification results, including report.</li> <li>Makes it possible to extend calibration intervals in accordance with operator's risk assessment.</li> </ul>

Device-specific accessories

# Accessories

For the transmitter

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Accessories	Description
Remote display	FHX50 housing to accommodate a display module → 🗎 61.
FHX50	<ul> <li>FHX50 housing suitable for:</li> <li>SD02 display module (push buttons)</li> <li>SD03 display module (touch control)</li> <li>Housing material: <ul> <li>Plastic PBT</li> <li>Stainless steel CF-3M (316L, 1.4404)</li> </ul> </li> <li>Length of connecting cable: up to max. 60 m (196 ft) (cable lengths available for order: 5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft))</li> </ul>
	<ul> <li>The measuring device can be ordered with the FHX50 housing and a display module. The following options must be selected in the separate order codes:</li> <li>Order code for measuring device, feature 030: Option L or M "Prepared for FHX50 display"</li> <li>Order code for FHX50 housing, feature 050 (device version): Option A "Prepared for FHX50 display"</li> <li>Order code for FHX50 housing, depends on the desired display module in featur 020 (display, operation): <ul> <li>Option C: for an SD02 display module (push buttons)</li> <li>Option E: for an SD03 display module (touch control)</li> </ul> </li> </ul>
	<ul> <li>The FHX50 housing can also be ordered as a retrofit kit. The measuring device display module is used in the FHX50 housing. The following options must be selected in the order code for the FHX50 housing:</li> <li>Feature 050 (measuring device version): option B "Not prepared for FHX50 display"</li> <li>Feature 020 (display, operation): option A "None, existing displayed used"</li> </ul>
	For details, see Special Documentation SD01007F
Overvoltage protection for 2-wire devices	Ideally, the overvoltage protection module should be ordered directly with the device. See product structure, characteristic 610 "Accessory mounted", option NA "Overvoltage protection". Separate order necessary only if retrofitting.
	<ul> <li>OVP10: For 1-channel devices (characteristic 020, option A):</li> <li>OVP20: For 2-channel devices (characteristic 020, options B, C, E or G)</li> </ul>
	For details, see Special Documentation SD01090F.
Weather protection cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight or extreme cold in winter.
	For details, see Special Documentation SD00333F

### For the sensor

Accessories	Description	
Seal set	For the regular replacement of seals for the sensor.	
Welding jig	Welded connection as process connection: welding jig for installation in pipe.	

Grounding rings	Are used to ground the fluid in lined measuring tubes to ensure proper measurement.  For details, see Installation Instructions EA00070D
Mounting kit	Consists of: • 2 process connections • Screws • Seals

Communication-specific accessories	Accessories	Description
accessories	Commubox FXA195	For intrinsically safe HART communication with FieldCare via the USB interface.
	HART	For details, see "Technical Information" TI00404F
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop.
		For details, see the "Technical Information" document TI405C/07
	HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.
		For details, see "Technical Information" TI00429F and Operating Instructions BA00371F
	Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity.
		For details, see Operating Instructions BA00061S
	Fieldgate FXA320	Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser.
		For details, see "Technical Information" TI00025S and Operating Instructions BA00053S
	Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser.
		For details, see "Technical Information" TI00025S and Operating Instructions BA00051S
	Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the <b>non-Ex area</b> .
		For details, see Operating Instructions BA01202S
	Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the <b>non-Ex area</b> and the <b>Ex area</b> .
		For details, see Operating Instructions BA01202S

Service-specific accessories	Accessories	Description
	Applicator	<ul> <li>Software for selecting and sizing Endress+Hauser measuring devices:</li> <li>Calculation of all the data needed to determine the optimum flowmeter: e.g. nominal diameter, pressure drop, performance characteristics or process connections.</li> <li>Graphic illustration of the calculation results</li> </ul>
		Administration, documentation and access to all project-related data and parameters throughout the entire life cycle of a project.
		<ul><li>Applicator is available:</li><li>Via the Internet: https://wapps.endress.com/applicator</li><li>On CD-ROM for local PC installation.</li></ul>

W@M	Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant information is available for every measuring device over time entire life cycle, such as the device status, spare parts, device-specific documentation, etc. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records. W@M is available: • Via the Internet: www.endress.com/lifecyclemanagement • On CD-ROM for local PC installation.	
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage the using the status information, it is also a simple but effective way of checking t status and condition. For details, see Operating Instructions BA00027S and BA00059S	

System components	Accessories	Description
	Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.
		For details, see "Technical Information" TI00133R and Operating Instructions BA00247R
	RN221N	Active barrier with power supply for safe separation of 4-20 mA standard signal circuits. Offers bidirectional HART transmission.
		For details, see "Technical Information" TI00073R and Operating Instructions BA00202R
	RNS221	Supply unit for powering two 2-wire measuring devices solely in the non-Ex area. Bidirectional communication is possible via the HART communication jacks.
		For details, see "Technical Information" TI00081R and Brief Operating Instructions KA00110R

# Documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

- The W@M Device Viewer : Enter the serial number from the nameplate (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

#### Standard documentation

**Brief Operating Instructions** 

Measuring device	Documentation code
Promag H 200	KA01120D

## **Operating Instructions**

Measuring device	Documentation code		
	HART	FOUNDATION Fieldbus	PROFIBUS PA
Promag H 200	BA01110D	BA01377D	BA01375D

#### **Device Parameters**

Measuring device	Documentation code		
	HART	FOUNDATION Fieldbus	PROFIBUS PA
Promag 200	GP01026D	GP01028D	GP01027D

#### Supplementary devicedependent documentation

### Safety Instructions

Contents	Documentation code
ATEX/IECEx Ex d[ia], Ex tb	XA01015D
ATEX/IECEx Ex ia, Ex tb	XA01016D
ATEX/IECEx Ex nA, Ex ic	XA01017D
cCSAus XP (Ex d)	XA01018D
cCSAus IS (Ex i)	XA01019D
NEPSI Ex d	XA01179D
NEPSI Ex i	XA01178D
NEPSI Ex nA, Ex ic	XA01180D
INMETRO Ex d	XA01309D
INMETRO Ex i	XA01310D
INMETRO Ex nA	XA01311D

#### Special Documentation

Contents	Documentation code
Functional Safety Manual	SD01451D
Heartbeat Technology	SD01452D

#### Installation Instructions

Contents	Documentation code
Installation Instructions for spare part sets	Specified for each individual accessory

# **Registered trademarks**

## HART®

Registered trademark of the HART Communication Foundation, Austin, USA

# **PROFIBUS®**

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

# FOUNDATION<sup>TM</sup> Fieldbus

Registration-pending trademark of the Fieldbus Foundation, Austin, Texas, USA

**Applicator**<sup>®</sup>, **FieldCare**<sup>®</sup>, **Field Xpert**<sup>TM</sup>, **HistoROM**<sup>®</sup>, **Heartbeat Technology**<sup>TM</sup> Registered or registration-pending trademarks of the Endress+Hauser Group

www.addresses.endress.com

