Technical Information **Proline Promag 50W, 53W**

Electromagnetic flowmeter





Flow measurement of liquids in water or wastewater applications

Application

Electromagnetic flowmeter for bidirectional measurement of liquids with a minimum conductivity of $\geq 5~\mu S/cm$:

- Drinking water
- Wastewater
- Sewage sludge
- Flow measurement up to 110000 m³/h (484315 gal/min)
- Fluid temperature up to +80 °C (+176 °F)
- Process pressures up to 40 bar (580 psi)
- Lengths in accordance with DVGW/ISO

Application-specific lining of the measuring pipe from polyurethane or hard rubber with the following drinking water permissions:

- KTW
- WRAS
- NSF
- ACS

Approvals for hazardous area:

- ATEX
- IECEx
- FM
- CSA
- NEPSI

Connection to process control system:

- HART
- PROFIBUS DP/PA
- FOUNDATION Fieldbus
- Modbus RS485

Your benefits

Promag measuring devices offer you cost-effective flow measurement with a high degree of accuracy for a wide range of process conditions.

The uniform Proline transmitter concept comprises:

- Modular device and operating concept resulting in a higher degree of efficiency
- Software options for batching, electrode cleaning and for measuring pulsating flow
- High degree of reliability and measuring stability
- Uniform operating concept

The tried-and-tested Promag sensors offer:

- No pressure loss
- Not sensitive to vibrations
- Simple installation and commissioning



Table of contents

unction and system design	
Measuring principle	3
Measuring system	3
nput	4
Measured variable	
Measuring ranges	
perable flow range	
nput signal	
- -	_
Output	4
Output signal	4
ignal on alarm	6
oad	
ow flow cutoff	
alvanic isolation	
witching output	6
Power supply	7
'erminal assignment	
upply voltage	
ower consumption	
ower supply failure	
Electrical connection, measuring unit	
llectrical connection,	
emote version	0
otential equalization	
able entries	1
lemote version cable specifications	2
Performance characteristics	2
deference operating conditions	
Maximum measured error	
repeatability	.)
nstallation1	4
Mounting location	4
Orientation	
nlet and outlet runs	6
Adapters 1	
ength of connecting cable 1	7
oundations, support	8.
'arrinanmant 1	0
Invironment 1	
Ambient temperature range	
torage temperature	
Degree of protection 1 hock and vibration resistance 1	
HOCK alla vibiation resistance	Ω
llectromagnetic compatibility (EMC)	
	9
Electromagnetic compatibility (EMC)	.9 0
Process	.9 0
Process 2 Medium temperature range 2 Conductivity 2 Pressure-temperature ratings 2	0
Process	.9 0 .0 .0 .0
Process 2 Medium temperature range 2 Conductivity 2 Pressure-temperature ratings 2	.9 0 .0 .0 .0


Limiting flow	24
Pressure loss	26
Vibrations	26
Mechanical construction	27
Design, dimensions	
Weight	
Measuring tube specifications	
Material	
Fitted electrodes	
Process connections	
Surface roughness	43
Operability	44
Local operation	
Language groups	
Remote operation	44
Certificates and approvals	45
CE mark \dots	
C-tick symbol	
Pressure measuring device approval	
Ex approval	45
Other standards and guidelines	
FOUNDATION Fieldbus certification	
Modbus RS485 certification	
PROFIBUS DP/PA certification	45
Ordering information	46
Accessories	46
	- `
Documentation	1. 6
Documentation	40
Registered trademarks	46

Function and system design

Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced is proportional to the flow velocity and is supplied to the amplifier by means of two measuring electrodes. The flow volume is calculated by means of the pipe cross-sectional area. The DC magnetic field is created through a switched direct current of alternating polarity.



 $Ue = B \cdot L \cdot v$ $Q = A \cdot v$

Ue Induced voltage

B Magnetic induction (magnetic field)

L Electrode spacing
v Flow velocity
Q Volume flow
A Pipe cross-section
I Current strength

Measuring system

The measuring system consists of a transmitter and a sensor.

Two versions are available:

- Compact version: Transmitter and sensor form a mechanical unit.
- Remote version: Sensor is mounted separate from the transmitter.

Transmitter:

- Promag 50 (user interface with push buttons for operation, two-line display, illuminated)
- Promag 53 ("Touch Control" without opening the housing, four-line display, unilluminated)

Sensor

Promag W (DN 25 to 2000 / 1 to 78")

Input

Measured variable	Flow velocity (proportional to induced voltage)			
Measuring ranges	Measuring ranges for liquids Typically $v = 0.01$ to 10 m/s (0.03 to 33 ft/s) with the specified accuracy			
Operable flow range	Over 1000 : 1			
Input signal	Status input (auxiliary input) ■ U = 3 to 30 V DC, R _i = 5 kΩ, galvanically isolated ■ Configurable for: totalizer(s) reset, measured value suppression, error-message reset			
	Status input (auxiliary input) with PROFIBUS DP and Modbus RS485 ■ U = 3 to 30 V DC, R _i = 3 kΩ, galvanically isolated ■ Switching level: 3 to 30 V DC, independent of polarity ■ Configurable for: totalizer(s) reset, measured value suppression, error-message reset, batching			

Current input (only Promag 53)

- Active/passive selectable, galvanically isolated, full scale value selectable, resolution: 3 μ A, temperature coefficient: typ. 0.005% o.r./°C (o.r. = of reading)
- Active: 4 to 20 mA, R_i £ 150 W, max. 24 V DC, short-circuit-proof
- \bullet Passive: 0/4 to 20 mA, R_i < 150 W, max. 30 V DC

start/stop (optional), batch totalizer reset (optional)

Output

Output signal

Promag 50

Current output

Active/passive selectable, galvanically isolated, time constant selectable (0.01 to 100 s), full scale value selectable, temperature coefficient: typ. 0.005% o.r./°C (o.r. = of reading), resolution: 0.5 mA

- Active: 0/4 to 20 mA, $R_L < 700 \Omega$ (HART: $R_L \ge 250 \Omega$)
- Passive: 4 to 20 mA, operating voltage V_S : 18 to 30 V DC, $R_i \ge 150~\Omega$

Pulse/frequency output

Passive, open collector, 30 V DC, 250 mA, galvanically isolated

- Frequency output: full scale frequency 2 to 1000 Hz (f_{max} = 1250 Hz), on/off ratio 1:1, pulse width max 10s
- Pulse output: pulse value and pulse polarity selectable, max. pulse width configurable (0.5 to 2000 ms)

PROFIBUS DP interface

- Transmission technology (Physical Layer): RS485 in accordance with ASME/TIA/EIA-485-A: 1998, galvanically isolated
- Profil version 3.0
- Data transmission rate: 9,6 kBaud to 12 MBaud
- Automatic data transmission rate recognition
- Function blocks: 1 × analog Input, 1 × totalizer
- Output data: volume flow, totalizer
- Input data: positive zero return (ON/OFF), totalizer control, value for local display
- Cyclic data transmission compatible with previous model Promag 33
- Bus address adjustable via miniature switches or local display (optional) at the measuring device

PROFIBUS PA interface

- Transmission technology (Physical Layer): IEC 61158-2 (MBP), galvanically isolated
- Profil version 3.0
- Current consumption: 11 mA
- Permissible supply voltage: 9 to 32 V
- Bus connection with integrated reverse polarity protection
- Error current FDE (Fault Disconnection Electronic): 0 mA
- Function blocks: $1 \times \text{analog input}$, $2 \times \text{totalizer}$
- Output data: volume flow, totalizer
- Input data: positive zero return (ON/OFF), control totalizer, value for local display

- Cyclic data transmission compatible with previous model Promag 33
- Bus address adjustable via miniature switches or local display (optional) at the measuring device

Promag 53

Current output

Active/passive selectable, galvanically isolated, time constant selectable (0.01 to 100 s), full scale value selectable, temperature coefficient: typ. 0.005% o.r./°C (o.r. = of reading), resolution: 0.5 mA

- Active: 0/4 to 20 mA, $R_I < 700 \Omega$ (HART: $R_I \ge 250 \Omega$)
- Passive: 4 to 20 mA, operating voltage V_S : 18 to 30 V DC, $R_i \ge 150 \Omega$

Pulse/frequency output

Active/passive selectable, galvanically isolated (Ex i version: only passive)

- Active: 24 V DC, 25 mA (max. 250 mA during 20 ms), $R_I > 100 \Omega$
- Passive: open collector, 30 V DC, 250 mA
- Frequency output: full scale frequency 2 to 10000 Hz (f_{max} = 12500 Hz), EEx-ia: 2 to 5000 Hz; on/off ratio 1:1, pulse width max. 10 s
- Pulse output: pulse value and pulse polarity selectable, max. pulse width configurable (0.05 to 2000 ms)

PROFIBUS DP interface

- Transmission technology (Physical Layer): RS485 in accordance with ASME/TIA/EIA-485-A: 1998, galvanically isolated
- Profil version 3.0
- Data transmission rate: 9,6 kBaud to 12 MBaud
- Automatic data transmission rate recognition
- Function blocks: 2 × analog Input, 3 × totalizer
- Output data: volume flow, calculated mass flow, totalizer 1 to 3
- Input data: positive zero return (ON/OFF), totalizer control, value for local display
- Cyclic data transmission compatible with previous model Promag 33
- Bus address adjustable via miniature switches or local display (optional) at the measuring device
- Available output combination → 🗎 7

PROFIBUS PA interface

- Transmission technology (Physical Layer): IEC 61158-2 (MBP), galvanically isolated
- Profil version 3.0
- Current consumption: 11 mA
- Permissible supply voltage: 9 to 32 V
- Bus connection with integrated reverse polarity protection
- Error current FDE (Fault Disconnection Electronic): 0 mA
- Function blocks: 2 × analog input, 3 × totalizer
- Output data: volume flow, calculated mass flow, totalizer 1 to 3
- Input data: positive zero return (ON/OFF), totalizer control, value for local display
- Cyclic data transmission compatible with previous model Promag 33
- Bus address adjustable via miniature switches or local display (optional) at the measuring device

Modbus RS485 interface

- Transmission technology (Physical Layer): RS485 in accordance with ASME/TIA/EIA-485-A: 1998, galvanically isolated
- Modbus device type: Slave
- Address range: 1 to 247
- Bus address adjustable via miniature switches or local display (optional) at the measuring device
- Supported Modbus function codes: 03, 04, 06, 08, 16, 23
- Broadcast: supported with the function codes 06, 16, 23
- Transfer mode: RTU or ASCII
- Supported baudrate: 1200, 2400, 4800, 9600, 19200, 38400, 57600, 115200 Baud
- Response time:
 - Direct data access = typically 25 to 50 ms
 - Auto-scan buffer (data range) = typically 3 to 5 ms
- Available output combination $\rightarrow \blacksquare 7$

FOUNDATION Fieldbus interface

- FOUNDATION Fieldbus H1
- Transmission technology (Physical Layer): IEC 61158-2 (MBP), galvanically isolated
- ITK version 5.01
- Current consumption: 12 mA
- Error current FDE (Fault Disconnection Electronic): 0 mA
- Bus connection with integrated reverse polarity protection
- Function blocks:
 - 5 × Analog Input (execution time: 18 ms each)
 - $-1 \times PID (25 ms)$
 - 1 × Digital Output (18 ms)
 - 1 × Signal Characterizer (20 ms)
 - 1 × Input Selector (20 ms)
 - 1 × Arithmetic (20 ms)
 - 1 × Integrator (18 ms)
- Output data: volume flow, calculated mass flow, temperature, totalizer 1 to 3
- Input data: positive zero return (ON/OFF), reset totalizer
- Link Master (LM) functionality is supported

Signal on alarm

- Current output [®] failure response selectable (e.g. in accordance with NAMUR recommendation NE 43)
- Pulse/frequency output [®] failure response selectable
- Status output (Promag 50) ® non-conductive by fault or power supply failure
- Relay output (Promag 53) ® de-energized by fault or power supply failure

Load

See "Output signal"

Low flow cutoff

Switch points for low flow cutoff are selectable.

Galvanic isolation

All circuits for inputs, outputs and power supply are galvanically isolated from each other.

Switching output

Status output (Promag 50, Promag 53)

Open collector, max. 30 V DC / 250 mA, galvanically isolated.

Configurable for: error messages, Empty Pipe Detection (EPD), flow direction, limit values.

Relay outputs (Promag 53)

Normally closed (NC or break) or normally open (NO or make) contacts available (default: relay 1 = NO, relay 2 = NC), max. 30 V / 0.5 A AC; 60 V / 0.1 A DC, galvanically isolated. Configurable for: error messages, Empty Pipe Detection (EPD), flow direction, limit values, batching contacts.

Power supply

Terminal assignment

Terminal assignment, Promag 50

Order code for	Terminal No. (inputs/outputs)							
"Input / Output"	20 (+) / 21 (-)	22 (+) / 23 (-)	24 (+) / 25 (-)	26 (+) / 27 (-)				
W	_	_	-	Current output HART				
A	-	_	Frequency output	Current output HART				
D	Status input	Status output	Frequency output	Current output HART				
Н	-	_	-	PROFIBUS PA				
J	_	-	+5 V (external termination)	PROFIBUS DP				
S	-	-	Frequency output, Ex i, passive	Current output, Ex i, passive, HART				
T	-	П	Frequency output, Ex i, passive	Current output, Ex i, passive, HART				

Terminal assignment, Promag 53

The inputs and outputs on the communication board can be either permanently assigned or variable, depending on the version ordered (see table). Replacements for modules which are defective or which have to be replaced can be ordered as accessories.

Order code for	Terminal No. (inputs/outputs)							
"Input / Output"	20 (+) / 21 (-)	22 (+) / 23 (-)	24 (+) / 25 (-)	26 (+) / 27 (-)				
Fixed communication l	ooards (fixed assig	nment)						
А	-	_	Frequency output	Current output HART				
В	Relay output 2	Relay output 1	Frequency output	Current output HART				
F	-	_	-	PROFIBUS PA, Ex i				
G	-	-	-	FOUNDATION Fieldbus, Ex i				
Н	-	_	-	PROFIBUS PA				
J	-	_	-	PROFIBUS DP				
K	-	_	-	FOUNDATION Fieldbus				
Q	_	_	Status input	Modbus RS485				
S	_	_	Frequency output, Ex i	Current output, Ex i, passive, HART				
T	_	_	Frequency output, Ex i	Current output, Ex i, passive, HART				
Flexible communicatio	n boards							
С	Relay output 2	Relay output 1	Frequency output	Current output HART				
D	Status input	Relay output	Frequency output	Current output HART				
L	Status input	Relay output 2	Relay output 1	Current output HART				
М	Status input	Frequency output	Frequency output	Current output HART				
N	Current output	Frequency output	Status input	Modbus RS485				
Р	Current output	Frequency output	Status input	PROFIBUS DP				
V	Relay output 2	Relay output 1	Status input	PROFIBUS DP				
2	Relay output	Current output	Frequency output	Current output HART				
4	Current input	Relay output	Frequency output	Current output HART				

Order code for "Input / Output"	Terminal No. (inputs/outputs)					
	20 (+) / 21 (-)	22 (+) / 23 (-)	24 (+) / 25 (-)	26 (+) / 27 (-)		
7	Relay output 2	Relay output 1	Status input	Modbus RS485		

Ground terminal → 🗎 9

Supply voltage

- 85 to 260 V AC, 45 to 65 Hz
- 20 to 55 V AC, 45 to 65 Hz
- 16 to 62 V DC

PROFIBUS PA and FOUNDATION Fieldbus

- Non-Ex: 9 to 32 V DC
- Ex i: 9 to 24 V DC
- Ex d: 9 to 32 V DC

Power consumption

- AC: < 15 VA (incl. sensor)
- DC: < 15 W (incl. sensor)

Switch-on current:


- Max. 3 A (< 5 ms) for 260 V AC
- Max. 13.5 A (< 50 ms) for 24 V DC

Power supply failure

Lasting min. $\frac{1}{2}$ cycle frequency: EEPROM saves measuring system data

- EEPROM or T-DAT (Promag 53 only) retain the measuring system data in the event of a power supply failure
- S-DAT: exchangeable data storage chip which stores the data of the sensor (nominal diameter, serial number, calibration factor, zero point etc.)

Electrical connection, measuring unit




Connecting the transmitter, cable cross-section max. 2.5 mm² (14 AWG)

- View A (field housing)
- В View B (stainless steel field housing)
- С View C (wall-mount housing)
- *) **) Fixed communication boards
- Flexible communication boards
- Connection compartment cover
- Cable for power supply: 85 to 260 V AC / 20 to 55 V AC / 16 to 62 V DC Terminal No. 1: L1 for AC, L+ for DC

 - Terminal No. 2: N for AC, L– for DC
- Fieldbus cable:
 - Terminal No. 26: DP (B) / PA + / FF + / Modbus RS485 (B) / (PA, FF: with polarity protection)
 Terminal No. 27: DP (A) / PA / FF / Modbus RS485 (A) / (PA, FF: with polarity protection)
- Ground terminal for Electrode cable shield / Fieldbus cable / RS485 line
- Service adapter for connecting service interface FXA193 (Fieldcheck, FieldCare)
 - Cable for external termination (only for PROFIBUS DP with fixed assignment communication board): - Terminal No. 24: +5 V - Terminal No. 25: DGND

Electrical connection, remote version



Connecting the remote version

- Wall-mount housing connection compartment
- Sensor connection housing cover Electrode cable b
- С
- Coil current cable d
- Not connected, insulated cable shields

Terminal no. and cable colors: 6/5 = brown; 7/8 = white; 4 = green; 36/37 = yellow

Potential equalization



Note!

The measuring system must be included in the potential equalization.

Perfect measurement is only ensured when the fluid and the sensor have the same electrical potential. This is ensured by the reference electrode integrated in the sensor as standard.

The following should also be taken into consideration for potential equalization:

- Internal grounding concepts in the company
- Operating conditions, such as the material/ grounding of the pipes (see table)

Standard situation

Operating conditions	Potential equalization
When using the measuring device in a: Metal, grounded pipe	
Potential equalization takes place via the ground terminal of the transmitter. Note! When installing in metal pipes, we recommend you connect the ground terminal of the transmitter housing with the piping.	
	Via the ground terminal of the transmitter

Special situations

Operating conditions

When using the measuring device in a:

• Metal pipe that is not grounded

This connection method also applies in situations where:

- Customary potential equalization cannot be ensured.
- Excessively high equalizing currents can be expected.


Both sensor flanges are connected to the pipe flange by means of a ground cable (copper wire, at least 6 mm² 0.0093 in²) and grounded. Connect the transmitter or sensor connection housing, as applicable, to ground potential by means of the ground terminal provided for the purpose.

- DN \leq 300 (12"): the ground cable is mounted directly on the conductive flange coating with the flange screws.
- DN \geq 350 (14"): the ground cable is mounted directly on the transportation metal support.



The ground cable for flange-to-flange connections can be ordered separately as an accessory from Endress+Hauser.

Potential equalization



Via the ground terminal of the transmitter and the flanges of the pipe


When using the measuring device in a:

- Plastic pipe
- Pipe with insulating lining

This connection method also applies in situations where:

- Customary potential equalization cannot be ensured.
- Excessively high equalizing currents can be expected.

Potential equalization takes place using additional ground disks, which are connected to the ground terminal via a ground cable (copper wire, at least 6 mm² / 0.0093 in²). When installing the ground disks, please comply with the enclosed Installation Instructions.



A0011895

Via the ground terminal of the transmitter and the optionally available ground disks


When using the measuring device in a:

• Pipe with a cathodic protection unit

The device is installed potential-free in the pipe. Only the two flanges of the pipe are connected with a ground cable (copper wire, at least $6 \text{ mm}^2 / 0.0093 \text{ in}^2$). Here, the ground cable is mounted directly on the conductive flange coating with flange screws.

Note the following when installing:

- The applicable regulations regarding potential-free installation must be observed.
- There should be **no** electrically conductive connection between the pipe and the device.
- The mounting material must withstand the applicable torques.



A0011896

Potential equalization and cathodic protection

Power supply isolation transformer Electrically isolated

Cable entries

Power supply and electrode cables (inputs/ outputs):

- Cable entry M20 × 1.5 (8 to 12 mm / 0.31 to 0.47")
- Sensor cable entry for armoured cables M20 × 1.5 (9.5 to 16 mm / 0.37 to 0.63")
- Thread for cable entries, ½" NPT, G ½"

Connecting cable for remote version:

- Cable entry M20 × 1.5 (8 to 12 mm / 0.31 to 0.47")
- Sensor cable entry for armoured cables M20 \times 1.5 (9.5 to 16 mm / 0.37 to 0.63")
- Thread for cable entries, ½" NPT, G ½"


Remote version cable specifications

Coil current cable

- $2 \times 0.75 \text{ mm}^2$ (18 AWG) PVC cable with common, braided copper shield ($\varnothing \sim 7 \text{ mm} / 0.28$ ")
- Conductor resistance: $\leq 37 \Omega/\text{km} (\leq 0.011 \Omega/\text{ft})$
- Capacitance core/core, shield grounded: ≤ 120 pF/m (≤ 37 pF/ft)
- Operating temperature: -20 to +80 °C (-68 to +176 °F)
- Cable cross-section: max. 2.5 mm² (14 AWG)
- Test voltage for cable insulation: \leq 1433 AC r.m.s. 50/60 Hz or \geq 2026 V DC

Electrode cable

- $3 \times 0.38 \text{ mm}^2$ (20 AWG) PVC cable with common, braided copper shield ($\varnothing \sim 7 \text{ mm} / 0.28$ ") and individual shielded cores
- With empty pipe detection (EPD): 4 × 0.38 mm² (20 AWG) PVC cable with common, braided copper shield ($\varnothing \sim 7$ mm / 0.28") and individual shielded cores
- Conductor resistance: $\leq 50 \Omega/\text{km} (\leq 0.015 \Omega/\text{ft})$
- Capacitance core/shield: ≤ 420 pF/m (≤ 128 pF/ft)
- Operating temperature: -20 to +80 °C (-68 to +176 °F)
- Cable cross-section: max. 2.5 mm² (14 AWG)



- Electrode cable Coil current cable b
- Core insulation
- 3 Core shield
- Core jacket
- Core reinforcement
- 6 7 Cable shield
- Outer jacket

Operation in zones of severe electrical interference

The measuring device complies with the general safety requirements in accordance with EN 61010 and the EMC requirements of IEC/EN 61326 and NAMUR recommendation NE 21.



Grounding is by means of the ground terminals provided for the purpose inside the connection housing. Ensure that the stripped and twisted lengths of cable shield to the ground terminal are as short as possible.

Performance characteristics

Reference operating conditions

As per DIN EN 29104 and VDI/VDE 2641:

- Fluid temperature: $+28 \,^{\circ}\text{C} \pm 2 \,^{\circ}\text{K}$ ($+82 \,^{\circ}\text{F} \pm 2 \,^{\circ}\text{K}$)
- Ambient temperature: +22 °C ±2 K (+72 °F ± 2 K)
- Warm-up period: 30 minutes

Installation conditions:

- Inlet run > 10 × DN
- Outlet run > 5 × DN
- Sensor and transmitter grounded.
- The sensor is centered in the pipe.

Maximum measured error


Promag 50:

- \blacksquare Current output: also typically ± 5 μA
- Pulse output: $\pm 0.5\%$ o.r. ± 1 mm/s ($\pm 0.5\%$ o.r. ± 0.04 in/s) optional: $\pm 0.2\%$ o.r. ± 2 mm/s ($\pm 0.2\%$ o.r. ± 0.08 in/s) (o.r. = of reading)

Promag 53:

- Current output: also typically \pm 5 μ A
- Pulse output: $\pm 0.2\%$ o.r. ± 2 mm/s ($\pm 0.2\%$ o.r. ± 0.08 in/s) (o.r. = of reading)

Fluctuations in the supply voltage do not have any effect within the specified range.



A0005531

Max. measured error in % of reading

Repeatability

Max. $\pm 0.1\%$ o.r. \pm 0.5 mm/s ($\pm 0.1\%$ o.r. \pm 0.02 in/s) (o.r. = of reading)

Installation


Mounting location

Mounting location

Entrained air or gas bubble formation in the measuring tube can result in an increase in measuring errors.

Avoid the following installation locations in the pipe:


- Highest point of a pipeline. Risk of air accumulating!
- Directly upstream from a free pipe outlet in a vertical pipeline.



Mounting location

Installation of pumps

Sensors may not be installed on the pump suction side. This precaution is to avoid low pressure and the consequent risk of damage to the lining of the measuring tube. Information on the pressure tightness of the measuring tube lining $\rightarrow \boxtimes 23$, Section "Pressure tightness".



Installation of pumps

Partially filled pipes


Partially filled pipes with gradients necessitate a drain-type configuration.

The empty pipe detection function (EPD) provides additional security in detecting empty or partially filled pipes.



Note!


Risk of solids accumulating. Do not install the sensor at the lowest point in the drain. It is advisable to install a cleaning valve.



Installation with partially filled pipes

Down pipes

Install a siphon or a vent valve downstream of the sensor in down pipes $h \ge 5$ m (16.4 ft). This precaution is to avoid low pressure and the consequent risk of damage to the lining of the measuring tube. This measure also prevents the liquid current stopping in the pipe which could cause air locks. Information on the pressure tightness of the measuring tube lining $\rightarrow \textcircled{1}{2}$ 23, Section "Pressure tightness".



Installation measures for vertical pipes


- 1 Vent valve
- 2 Pipe siphon
- h Length of the down pipe

Orientation

An optimum orientation helps avoid gas and air accumulations and deposits in the measuring tube. However, the measuring device also offers the additional function of empty pipe detection (EPD) for detecting partially filled measuring tubes or if outgassing fluids or fluctuating operating pressures are present.

Vertical orientation

This is the ideal orientation for self-emptying piping systems and for use in conjunction with empty pipe detection.




Vertical orientation

Horizontal orientation

The measuring electrode axis should be horizontal. This prevents brief insulation of the two measuring electrodes by entrained air bubbles.



Empty pipe detection only works correctly with horizontal orientation if the transmitter housing is facing upwards. Otherwise there is no guarantee that empty pipe detection will respond if the measuring tube is only partially filled or empty.



Horizontal orientation


- ${\it EPD \ electrode \ for \ empty \ pipe \ detection}$
- Measuring electrodes for signal detection Reference electrode for potential equalization

Inlet and outlet runs

If possible, install the sensor well clear of assemblies such as valves, T-pieces, elbows etc.

Note the following inlet and outlet runs to comply with measuring accuracy specifications:

- Inlet run: \geq 5 × DN
- Outlet run: ≥ 2 × DN



Inlet and outlet run

Adapters


Suitable adapters to DIN EN 545 (double-flange reducers) can be used to install the sensor in largerdiameter pipes. The resultant increase in the rate of flow improves measuring accuracy with very slowmoving fluids. The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders.



Note!

The nomogram only applies to liquids of viscosity similar to water.

- Calculate the ratio of the diameters d/D.
- 2. From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.




Pressure loss due to adapters

Length of connecting cable

When mounting the remote version, please note the following to achieve correct measuring results:

• Fix cable run or lay in armored conduit. Cable movements can falsify the measuring signal especially in the case of low fluid conductivities.

- Route the cable well clear of electrical machines and switching elements.
- If necessary, ensure potential equalization between sensor and transmitter.
- The permitted cable length L_{max} is determined by the fluid conductivity. A minimum conductivity of 20 μ S/cm is required for measuring demineralized water.
- When the empty pipe detection function is switched on (EPD), the maximum connecting cable length is 10 m (33 ft).



Permitted length of connecting cable for remote version Area marked in gray = permitted range; L_{max} = length of connecting cable in [m] ([ft]); fluid conductivity in $[\mu S/cm]$


Foundations, support

If the nominal diameter is DN \geq 350, mount the transmitter on a foundation of adequate load-bearing strength.



Note!

Do not allow the casing to take the weight of the sensor. This would buckle the casing and damage the internal magnetic coils.



Environment

Ambient temperature range

Transmitter

- Standard: -20 to +60 °C (-4 to +140 °F)
- Optional: -40 to +60 °C (-40 to +140 °F)



Note

At ambient temperatures below -20 °C (-4 °F)the readability of the display may be impaired.

Sensor

- Flange material carbon steel: -10 to +60 °C (14 to +140 °F)
- Flange material stainless steel: -40 to +60 °C (-40 to +140 °F)



Notel

The permitted temperature range of the measuring tube lining may not be undershot or overshot $\rightarrow \cong 20$, Section "Medium temperature range".

Please note the following points:

- Install the device in a shady location. Avoid direct sunlight, particularly in warm climatic regions.
- The transmitter must be mounted separate from the sensor if both the ambient and fluid temperatures are high.

Storage temperature

The storage temperature corresponds to the operating temperature range of the measuring transmitter and the appropriate measuring sensors.



Note!

- The measuring device must be protected against direct sunlight during storage in order to avoid unacceptably high surface temperatures.
- A storage location must be selected where moisture does not collect in the measuring device. This
 will help prevent fungus and bacteria infestation which can damage the liner.
- Do not remove the protective plates or caps on the process connections until the device is ready to install.

Degree of protection

- Standard: IP 67 (NEMA 4X) for transmitter and sensor.
- Optional: IP 68 (NEMA 6P) for sensor for remote version.
- For information regarding applications where the device is buried directly in the soil or is installed in a flooded wastewater basin please contact your local Endress+Hauser Sales Center.

Shock and vibration resistance

Acceleration up to 2 g following IEC 600 68-2-6

Electromagnetic compatibility (EMC)

As per IEC/EN 61326 and NAMUR recommendation NE 21.

Process

Medium temperature range

The permitted temperature depends on the lining of the measuring tube:

- Polyurethane: -20 to +50 °C (-4 to +122 °F) (DN 25 to 1200 / 1 to 48")
- Hard rubber: ±0 to +80 °C (+32 to +176 °F) (DN 50 to 2000 / 2 to 78")

Conductivity

The minimum conductivity is:

- \geq 5 µS/cm for fluids generally
- \geq 20 µS/cm for demineralized water



In the remote version, the necessary minimum conductivity also depends on the cable length

Pressure-temperature ratings




Note!

The following diagrams contain material load diagrams (reference curves) for flange materials with regard to the medium temperature. However, the maximum medium temperatures permitted always depend on the lining material of the sensor and/or the sealing material ($\rightarrow \stackrel{\triangle}{=} 20$).


Flange connection to EN 1092-1 (DIN 2501)

Material: S235JRG2, S235JR+N, P250GH, P245GH, E250C, A105




Flange connection to EN 1092-1 (DIN 2501)

Material: 1.4571, 1.4404, F316L




Flange connection to ASME B16.5

Material: A 105




Flange connection to ASME B16.5

Material: F316L



Flange connection to AWWA C 207, Class D $\,$


Material: A105, A181 Cl.70, P265GH, S275JR, E250C, S235JRG2



A0034681-FN

Flange connection to JIS B2220


Material: A105, A350 LF2, F316L



A0021183-EN

Flange connection to AS 2129 Table E


Material: A105, P235GH, P265GH, S235JRG2



A0021189-EI

Flange connection to AS 4087 PN 16

Material: A105, P265GH, S275JR



Medium pressure range (nominal pressure)

- EN 1092-1 (DIN 2501)
 - PN 6 (DN 350 to 2000 / 14 to 78")
 - PN 10 (DN 200 to 2000 / 8 to 78")
 - PN 16 (DN 65 to 2000 / 3 to 78")
 - PN 25 (DN 200 to 1000 / 8 to 40")
 - PN 40 (DN 25 to 150 / 1 to 6")
- ASME B 16.5
 - Class 150 (DN 1 to 24")
 - Class 300 (DN 1 to 6")
- AWWA C2072
 - Class D (DN 28 to 78")
- JIS B2220
 - 10K (DN 50 to 750 / 2 to 30")
 - 20K (DN 25 to 600 / 1 to 24")
- AS 2129
 - Table E (DN 80, 100, 150 to 400, 500, 600 / 3", 4", 6 to 16", 20", 24")
- AS 4087
 - PN 16 (DN 80, 100, 150 to 400, 500, 600 / 3", 4", 6 to 16", 20", 24")

Pressure tightness

Measuring tube lining: Polyurethane

Nominal	diameter	Limit values for abs. pressure [mbar] ([psi]) at fluid temperatures:				
		25 °C ((77 °F)	50 °C (122 °F)		
[mm]	[inch]	[mbar]	[psi]	[mbar]	[psi]	
25 to 1200	1 to 48"	0	0	0	0	

Measuring tube lining: Hard rubber

Nominal	diameter	Limit values for abs. pressure [mbar] ([psi]) at fluid temperatures:					tures:
		25 °C (25 °C (77 °F) 50 °C (122 °F) 80 °C (176 °C)		7°F) 50°C (122°F)		
[mm]	[inch]	[mbar]	[psi]	[mbar]	[psi]	[mbar]	[psi]
50 to 2000	2 to 78"	0	0	0	0	0	0

Limiting flow

The diameter of the pipe and the flow rate determine the nominal diameter of the sensor. The optimum flow velocity is between 2 to 3 m/s (6.5 to 9.8 ft/s). The velocity of flow (v), moreover, has to be matched to the physical properties of the fluid:

- v < 2 m/s (6.5 ft/s): for abrasive fluids such as potter's clay, lime milk, ore slurry etc.
- v > 2 m/s (6.5 ft/s): for fluids causing build-up such as wastewater sludges etc.

Dian	neter	Recommende			Factory sett	ings				
		Min./max. full sca	le value		le value t output	Pulse v	alue	Low flow		
[mm]	[inch]	(v ~ 0.3 or 10 m/s	;)		5 m/s)	(~ 2 puls	ses/s)	(v ~ C	0.04 m/s	
25	1"	9 to 300	dm³/ min	75	dm³/min	0.50	dm³	1	dm³/mi	
32	-	15 to 500	dm³/ min	125	dm³/min	1.00	dm³	2	dm³/mi	
40	1½"	25 to 700	dm³/ min	200	dm³/min	1.50	dm³	3	dm³/mi	
50	2"	35 to 1100	dm³/ min	300	dm³/min	2.50	dm³	5	dm³/mi	
65	-	60 to 2000	dm³/ min	500	dm³/min	5.00	dm³	8	dm³/mi	
80	3"	90 to 3000	dm³/ min	750	dm³/min	5.00	dm³	12	dm³/mi	
100	4"	145 to 4700	dm³/ min	1200	dm³/min	10.00	dm³	20	dm³/mi	
125	-	220 to 7500	dm³/ min	1850	dm³/min	15.00	dm³	30	dm³/mi	
150	6"	20 to 600	m³/h	150	m³/h	0.025	m^3	2.5	m³/h	
200	8"	35 to 1100	m³/h	300	m³/h	0.05	m ³	5.0	m³/h	
250	10"	55 to 1700	m³/h	500	m³/h	0.05	m^3	7.5	m³/h	
300	12"	80 to 2400	m³/h	750	m³/h	0.10	m^3	10	m³/h	
350	14"	110 to 3300	m³/h	1000	m³/h	0.10	m^3	15	m³/h	
375	15"	140 to 4200	m³/h	1200	m³/h	0.15	m^3	20	m³/h	
400	16"	140 to 4200	m³/h	1200	m³/h	0.15	m^3	20	m³/h	
450	18"	180 to 5400	m³/h	1500	m³/h	0.25	m³	25	m³/h	
500	20"	220 to 6600	m³/h	2000	m³/h	0.25	m ³	30	m³/h	
600	24"	310 to 9600	m³/h	2500	m³/h	0.30	m ³	40	m³/h	
700	28"	420 to 13500	m³/h	3500	m³/h	0.50	m³	50	m³/h	
-	30"	480 to 15000	m³/h	4000	m³/h	0.50	m^3	60	m³/h	
800	32"	550 to 18000	m³/h	4500	m³/h	0.75	m^3	75	m³/h	
900	36"	690 to 22500	m³/h	6000	m³/h	0.75	m^3	100	m³/h	
1000	40"	850 to 28000	m³/h	7000	m³/h	1.00	m^3	125	m³/h	
-	42"	950 to 30000	m³/h	8000	m³/h	1.00	m^3	125	m³/h	
1200	48"	1250 to 40000	m³/h	10000	m³/h	1.50	m^3	150	m³/h	
-	54"	1550 to 50000	m³/h	13000	m³/h	1.50	m^3	200	m³/h	
1400	-	1700 to 55000	m³/h	14000	m³/h	2.00	m ³	225	m³/h	
-	60"	1950 to 60000	m³/h	16000	m³/h	2.00	m ³	250	m³/h	
1600	-	2200 to 70000	m³/h	18000	m³/h	2.50	m ³	300	m³/h	
_	66"	2500 to 80000	m³/h	20500	m³/h	2.50	m ³	325	m³/h	

Flow characteristic values (SI units)									
Dian	neter	Recommended flow	Factory settings						
		Min./max. full scale value	Full scale value Current output	Pulse value	Low flow				
[mm]	[inch]	(v ~ 0.3 or 10 m/s)	(v ~ 2.5 m/s)	(~ 2 pulses/s)	(v ~ 0.04 m/s)				
1800	72"	2800 to 90000 m ³ /h	23000 m ³ /h	3.00 m ³	350 m ³ /h				
-	78"	3300 to 100000 m ³ /h	28500 m ³ /h	3.50 m ³	450 m ³ /h				
2000	-	3400 to 110000 m ³ /h	28500 m ³ /h	3.50 m ³	450 m ³ /h				

Flow characteristic values (US units)											
Dian	neter	Recommended	flow rate		F	actory set	tings				
		Min./max. full scale value Full scale value Current output		Min./max. full scale value				Pulse	value	Lo	w flow
[inch]	[mm]	(v ~ 0.3 or 1	.0 m/s)	(v ~ 2.	5 m/s)	(~ 2 pul	ses/s)	(v ~ C).04 m/s)		
1"	25	2.5 to 80	gal/min	18	gal/min	0.20	gal	0.25	gal/min		
-	32	4 to 130	gal/min	30	gal/min	0.20	gal	0.50	gal/min		
1½"	40	7 to 190	gal/min	50	gal/min	0.50	gal	0.75	gal/min		
2"	50	10 to 300	gal/min	75	gal/min	0.50	gal	1.25	gal/min		
-	65	16 to 500	gal/min	130	gal/min	1	gal	2.0	gal/min		
3"	80	24 to 800	gal/min	200	gal/min	2	gal	2.5	gal/min		
4"	100	40 to 1250	gal/min	300	gal/min	2	gal	4.0	gal/min		
-	125	60 to 1950	gal/min	450	gal/min	5	gal	7.0	gal/min		
6"	150	90 to 2650	gal/min	600	gal/min	5	gal	12	gal/min		
8"	200	155 to 4850	gal/min	1200	gal/min	10	gal	15	gal/min		
10"	250	250 to 7500	gal/min	1500	gal/min	15	gal	30	gal/min		
12"	300	350 to 10600	gal/min	2400	gal/min	25	gal	45	gal/min		
14"	350	500 to 15000	gal/min	3600	gal/min	30	gal	60	gal/min		
15"	375	600 to 19000	gal/min	4800	gal/min	50	gal	60	gal/min		
16"	400	600 to 19000	gal/min	4800	gal/min	50	gal	60	gal/min		
18"	450	800 to 24000	gal/min	6000	gal/min	50	gal	90	gal/min		
20"	500	1000 to 30000	gal/min	7500	gal/min	75	gal	120	gal/min		
24"	600	1400 to 44000	gal/min	10500	gal/min	100	gal	180	gal/min		
28"	700	1900 to 60000	gal/min	13500	gal/min	125	gal	210	gal/min		
30"	-	2150 to 67000	gal/min	16500	gal/min	150	gal	270	gal/min		
32"	800	2450 to 80000	gal/min	19500	gal/min	200	gal	300	gal/min		
36"	900	3100 to 100000	gal/min	24000	gal/min	225	gal	360	gal/min		
40"	1000	3800 to 125000	gal/min	30000	gal/min	250	gal	480	gal/min		
42"	_	4200 to 135000	gal/min	33000	gal/min	250	gal	600	gal/min		
48"	1200	5500 to 175000	gal/min	42000	gal/min	400	gal	600	gal/min		
54"	-	9 to 300	Mgal/min	75	Mgal/min	0.0005	Mgal	1.3	Mgal/min		
-	1400	10 to 340	Mgal/min	85	Mgal/min	0.0005	Mgal	1.3	Mgal/min		
60"	-	12 to 380	Mgal/min	95	Mgal/min	0.0005	Mgal	1.3	Mgal/min		

Flow ch	aracteris	tic values (US units)			
Dian	neter	Recommended flow rate	F	actory settings	
		Min./max. full scale value	Full scale value Current output	Pulse value	Low flow
[inch]	[mm]	(v ~ 0.3 or 10 m/s)	(v ~ 2.5 m/s)	(~ 2 pulses/s)	(v ~ 0.04 m/s)
-	1600	13 to 450 Mgal/min	110 Mgal/min	0.0008 Mgal	1.7 Mgal/min
66"	1	14 to 500 Mgal/min	120 Mgal/min	0.0008 Mgal	2.2 Mgal/min
72"	1800	16 to 570 Mgal/min	140 Mgal/min	0.0008 Mgal	2.6 Mgal/min
78"	1	18 to 650 Mgal/min	175 Mgal/min	0.001 Mgal	3.0 Mgal/min
-	2000	20 to 700 Mgal/min	175 Mgal/min	0.001 Mgal	3.0 Mgal/min

Pressure loss


- No pressure loss if the sensor is installed in a pipe with the same nominal diameter.

Vibrations

Secure the piping and the sensor if vibration is severe.



Note!




Measures to prevent vibration of the measuring device

L > 10 m (33 ft)

Mechanical construction

Design, dimensions

Transmitter remote version, wall-mount housing (non Ex-zone and II3G/Zone 2)



A0001150

Dimensions (SI units)

А	В	С	D	Е	F	G	Н	J
215	250	90.5	159.5	135	90	45	> 50	81
K	L	M	N	0	Р	Q	R	S
53	95	53	102	81.5	11.5	192	8 × M5	20


All dimensions in [mm]

Dimensions (US units)

А	В	С	D	Е	F	G	Н	J
8.46	9.84	3.56	6.27	5.31	3.54	1.77	> 1.97	3.18
K	L	M	N	0	Р	Q	R	S
2.08	3.74	2.08	4.01	3.20	0.45	7.55	8 × M5	0.79

All dimensions in [inch]

Transmitter remote version, connection housing (II2GD/Zone 1)



A0002128

Dimensions (SI units)

А	A*	В	В*	С	D	Е	ØF	G	Н	J	К	L	М
265	242	240	217	206	186	178	8.6 (M8)	100	130	100	144	170	355

All dimensions in [mm]

Dimensions (US units)


Α	A*	В	В*	С	D	Е	ØF	G	Н	J	K	L	M
10.4	9.53	9.45	8.54	8.11	7.32	7.01	0.34 (M8)	3.94	5.12	3.94	5.67	6.69	14.0

All dimensions in [inch]

There is a separate mounting kit for the wall-mounted housing. It can be ordered from Endress+Hauser as an accessory. The following installation variants are possible:


- Panel-mounted installation
- Pipe mounting

Installation in control panel




Engineering unit mm (in)

Pipe mounting



Engineering unit mm (in)

Compact version DN ≤ 300 (12")



Dimensions (SI units)

DN	L 1)	А	A*	В	С	D	Е	F	G	Н	К
EN (DIN) / JIS / AS 2)											
25	200						341	257	84	94	120
32	200						341	257	84	94	120
40	200						341	257	84	94	120
50	200						341	257	84	94	120
65	200						391	282	109	94	180
80	200	227	207	107	160	160	391	282	109	94	180
100	250	227	207	187	168	160	391	282	109	94	180
125	250						472	322	150	140	260
150	300						472	322	150	140	260
200	350						527	347	180	156	324
250	450						577	372	205	166	400
300	500						627	397	230	166	460


¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
²⁾ For flanges to AS, only the nominal diameters DN 80, 100 and 150 to 300 are available. All dimensions in [mm]

Dimensions (US units)

DN	L 1)	А	A*	В	С	D	Е	F	G	Н	К
ASME											
1"	7.87						13.4	10.1	3.31	3.70	4.72
1½"	7.87						13.4	10.1	3.31	3.70	4.72
2"	7.87						13.4	10.1	3.31	3.70	4.72
3"	7.87						15.4	11.1	4.29	3.70	7.09
4"	9.84	8.94	8.15	7.36	6.61	6.30	15.4	11.1	4.29	3.70	7.09
6"	11.8						18.6	12.7	5.91	5.51	10.2
8"	13.8						20.8	13.7	7.09	6.14	12.8
10"	17.7						22.7	14.7	8.07	6.14	15.8
12"	19.7						24.7	15.6	9.06	6.54	18.1

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW. All dimensions in [inch]

Compact version DN \geq 350 (14")



Dimensions (SI units)

DN EN (DIN) / AS ²⁾	L 1)	A	A*	В	С	D	E	F	G	Н	J
350	550						738.5	456.5	282.0	288	564
375	600						790.5	482.5	308.0	288	616
400	600						790.5	482.5	308.0	288	616
450	650						840.5	507.5	333.0	292	666
500	650						891.5	533.0	358.5	292	717
600	780						995.5	585.0	410.5	402	821
700	910						1198.5	686.5	512.0	589	1024
750	975						1198.5	686.5	512.0	626	1024
800	1040						1241.5	708.5	533.5	647	1067
900	1170	227	207	187	168	160	1394.5	784.5	610.0	785	1220
1000	1300	227	207	107	100	100	1546.5	860.5	686.0	862	1372
1050	1365						1598.5	886.5	712.0	912	1424
1200	1560						1796.5	985.5	811.0	992	1622
1350	1755						1998.5	1086.5	912.0	1252	1824
1400	1820						2148.5	1161.5	987.0	1252	1974
1500	1950						2196.5	1185.5	1011.0	1392	2022
1600	2080						2286.5	1230.5	1056.0	1482	2112
1650	2145						2360.5	1267.5	1093.0	1482	2186
1800	2340						2550.5	1362.5	1188.0	1632	2376
2000	2600						2650.5	1412.5	1238.0	1732	2476


¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
²⁾ For flanges to AS, only DN 350, 400, 500 and 600 are available.
All dimensions in [mm]

Dimensions (US units)

DN	L 1)	А	A*	В	С	D	Е	F	G	Н	J
ASME / AWWA 2)											
14"	21.6						29.1	17.9	11.1	11.3	22.2
15"	23.6						31.1	18.9	12.1	11.3	24.2
16"	23.6						31.1	18.9	12.1	11.3	24.2
18"	25.6						33.1	19.9	13.1	11.5	26.2
20"	25.6						35.1	20.9	14.1	11.5	28.2
24"	30.7						39.2	23.0	16.2	15.8	32.3
28"	35.8						47.2	27.0	20.1	23.2	40.3
30"	38.4						47.2	27.0	20.1	24.6	40.3
32"	40.9						48.9	27.9	21.0	25.5	42.0
36"	46.0	8.94	0.15	7.26	6.61	6.20	54.9	30.9	24.0	30.9	48.0
40"	51.2	6.94	8.15	7.36	6.61	6.30	60.9	33.9	27.0	33.9	54.0
42"	53.7						62.9	34.9	28.0	35.9	56.0
48"	61.4						71.7	38.8	31.9	39.0	63.8
54"	69.1						78.7	42.8	35.9	42.3	71.8
56"	71.7						84.6	45.7	38.9	49.3	77.7
60"	76.8						86.5	46.7	39.8	54.8	79.6
64"	81.9						90.0	48.4	41.6	58.4	83.2
66"	84.4						92.9	49.9	43.0	58.4	86.0
72"	92.1						100.4	53.6	46.8	64.2	93.5
78"	102.3						104.3	55.6	48.7	68.2	97.5

 $^{^{1)}}$ The length is regardless of the pressure rating selected. Fitting length to DVGW. $^{2)}$ Flanges $\leq 24"$ only to ASME available, $\geq 28"$ only to AWWA available. All dimensions in [inch]

Sensor, remote version DN ≤ 300 (12")



Dimensions (SI units)

DN	L 1)	А	В	С	D	Е	F	G	Н	J
EN (DIN) / JIS / AS ²⁾										
25	200	129	163	143	102	286	202	84	120	94
32	200	129	163	143	102	286	202	84	120	94
40	200	129	163	143	102	286	202	84	120	94
50	200	129	163	143	102	286	202	84	120	94
65	200	129	163	143	102	336	227	109	180	94
80	200	129	163	143	102	336	227	109	180	94
100	250	129	163	143	102	336	227	109	180	94
125	250	129	163	143	102	417	267	150	260	140
150	300	129	163	143	102	417	267	150	260	140
200	350	129	163	143	102	472	292	180	324	156
250	450	129	163	143	102	522	317	205	400	166
300	500	129	163	143	102	572	342	230	460	166


¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
²⁾ For flanges to AS, only the nominal diameters DN 80, 100 and 150 to 300 are available.
All dimensions in [mm]

Dimensions (US units)

DN	L 1)	А	В	С	D	Е	F	G	Н	J
ASME										
1"	7.87	5.08	6.42	5.63	4.02	11.3	7.95	3.32	4.72	3.70
1½"	7.87	5.08	6.42	5.63	4.02	11.3	7.95	3.32	4.72	3.70
2"	7.87	5.08	6.42	5.63	4.02	11.3	7.95	3.32	4.72	3.70
3"	7.87	5.08	6.42	5.63	4.02	13.2	8.94	4.30	7.10	3.70
4"	9.84	5.08	6.42	5.63	4.02	13.2	8.94	4.30	7.10	3.70
6"	11.8	5.08	6.42	5.63	4.02	16.4	10.5	5.91	10.2	5.51
8"	13.8	5.08	6.42	5.63	4.02	18.6	11.5	7.10	12.8	6.14
10"	17.7	5.08	6.42	5.63	4.02	20.6	12.5	8.08	15.8	6.14
12"	19.7	5.08	6.42	5.63	4.02	22.5	13.5	9.06	18.1	6.54

 $^{^{1)}}$ The length is regardless of the pressure rating selected. Fitting length to DVGW. All dimensions in [inch]

Sensor, remote version DN ≥ 350 (14")



Dimensions (SI units)

DN	L 1)	А	В	С	D	Е	F	G	Н	J
EN (DIN) / AS 2)										
350	550					683.5	401.5	282.0	564	288
375	600					735.5	427.5	308.0	616	288
400	600					735.5	427.5	308.0	616	288
450	650					785.5	452.5	333.0	666	292
500	650					836.5	478.0	358.5	717	292
600	780					940.5	530.0	410.5	821	402
700	910					1143.5	631.5	512.0	1024	589
750	975					1143.5	631.5	512.0	1024	626
800	1040					1186.5	653.0	533.5	1067	647
900	1170	129	163	143	102	1339.5	729.5	610.0	1220	785
1000	1300	129	105	145	102	1491.5	805.5	686.0	1372	862
1050	1365					1543.5	831.5	712.0	1424	912
1200	1560					1741.5	930.5	811.0	1622	992
1350	1755					1943.5	1031.5	912.0	1824	1252
1400	1820					2093.5	1106.5	987.0	1974	1252
1500	1950					2141.5	1130.5	1011.0	2022	1392
1600	2080					2231.5	1175.5	1056.0	2112	1482
1650	2145					2305.5	1212.5	1093.0	2186	1482
1800	2340					2495.5	1307.5	1188.0	2376	1632
2000	2600					2595.5	1357.5	1238.0	2476	1732


¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW. ²⁾ For flanges to AS, only DN 350, 400, 500 and 600 are available. All dimensions in [mm]

Dimensions (US units)

DN ASME / AWWA ²⁾	L 1)	A	В	С	D	Е	F	G	Н	J
14"	21.6					29.1	15.8	11.1	22.2	11.3
15"	23.6					31.1	16.8	12.1	24.2	11.3
16"	23.6					31.1	16.8	12.1	24.2	11.3
18"	25.6					33.1	17.8	13.1	26.2	11.5
20"	25.6					35.1	18.8	14.1	28.2	11.5
24"	30.7					39.2	20.9	16.2	32.3	15.8
28"	35.8					45.0	24.9	20.1	40.3	23.2
30"	38.4					45.0	24.9	20.1	40.3	24.6
32"	40.9					46.7	25.7	21.0	42.0	25.5
36"	46.0	5.08	6.40	E 62	4.02	52.7	28.7	24.0	48.0	30.9
40"	51.2	5.00	6.42	5.63	4.02	58.7	31.7	27.0	54.0	33.9
42"	53.7					60.7	32.7	28.0	56.0	35.9
48"	61.4					68.5	36.6	31.9	63.8	39.0
54"	69.1					76.5	40.6	35.9	71.8	42.3
56"	71.7					82.4	43.6	38.9	77.7	49.3
60"	76.8					84.3	44.5	39.8	79.6	54.8
64"	81.9					87.9	46.3	41.6	83.2	58.4
66"	84.4					90.8	47.7	43.0	86.0	58.4
72"	92.1					98.2	51.5	46.8	93.5	64.2
78"	102.3					102.2	53.4	48.7	97.5	68.2

 $^{^{1)}}$ The length is regardless of the pressure rating selected. Fitting length to DVGW. $^{2)}$ Flanges $\leq 24"$ only to ASME available, $\geq 28"$ only to AWWA available. All dimensions in [inch]

Ground disk for flange connections



Dimensions (SI units)

DN ¹⁾	A	В	С	D	E	t
EN (DIN) / JIS / AS ²⁾						
25	26	62	77.5	87.5		
32	35	80	87.5	94.5		
40	41	82	101	103		
50	52	101	115.5	108		
65	68	121	131.5	118		
80	80	131	154.5	135	6.5	2
100	104	156	186.5	153		
125	130	187	206.5	160		
150	158	217	256	184		
200	206	267	288	205		
250	260	328	359	240		
300 ³⁾	312	375	413	273		
300 ⁴⁾	310	375	404	268		
350 ³⁾	343	433	479	365		
375 ³⁾	393	480	542	395		
400 ³⁾	393	480	542	395	9.0	
450 ³⁾	439	538	583	417	9.0	
500 ³⁾	493	592	650	460		
600 ³⁾	593	693	766	522		

¹⁾ Ground disks can be used for all flange standards/pressure ratings that can be delivered, except for DN ≥ 300.
2) Only DN 32, 40, 65 and 125 are available for flanges according to AS.
3) PN 10/16
4) PN 25, JIS 10K/20K

All dimensions in [mm]

Dimensions (US units)

DN ¹⁾ ASME	А	В	С	D	Е	t
1"	1.02	2.44	3.05	3.44		
1½"	1.61	3.23	3.98	4.06		
2"	2.05	3.98	4.55	4.25		
3"	3.15	5.16	6.08	5.31		
4"	4.09	6.14	7.34	6.02	0.26	
6"	6.22	8.54	10.08	7.24		
8"	8.11	10.5	11.3	8.07		
10"	10.2	12.9	14.1	9.45		0.08
12"	12.3	14.8	16.3	10.8		
14"	13.5	17.1	18.9	14.4		
15"	15.45	18.9	21.3	15.6		
16"	15.45	18.9	21.3	15.6	0.35	
18"	17.3	21.2	23.0	16.4	0.55	
20"	19.4	23.3	25.6	18.1		
24"	23.4	27.3	30.1	20.6		

¹⁾ Ground disks can be used for all flange standards/pressure ratings. All dimensions in [inch]

Weight

Weight in SI units

Weight data in kg															
Nomin			C	omp	act version	on		Remote version (without cable)						able)	
diamet	er							Sensor Transm						Transmitter	
[mm]	[inch]	EN	(DIN) / AS ¹⁾		JIS	IS ASME / AWWA		EN (DIN) / AS ¹⁾			JIS		SME / .WWA	Wall-mount housing	
25	1"		7.3		7.3		7.3		5.3		5.3		5.3		
32	-	40	8.0		7.3		-	40	6.0		5.3		-		
40	1½"	PN	9.4		8.3		9.4	PN	7.4		6.3		7.4		
50	2"		10.6		9.3		10.6		8.6		7.3		8.6		
65	-		12		11.1		-		10.0		9.1		-		
80	3"	_	14		112.5		14.0	_	12.0		10.5		12.0		
100	4"	PN 16	16		14.7		16.0	PN 16	14.0		12.7		14.0		
125	-	ц	21.5		21.0		-	Ч	19.5		19.0		-		
150	6"		25.5		24.5	150	25.5		23.5		22.5	150	23.5		
200	8"	0	45		41.9	Class	45	0	43		39.9	Class	43		
250	10"	PN 10	65		69.4		75	PN 10	63		67.4		73		
300	12"	Щ	70		72.3		110	Щ	68		70.3		108		
350	14"		105		81.1	175		103		79.1		173			
375	15"		120		-		-	118		-		-			
400	16"		120		102	-	205		118		100		203		
450	18"		161		130		-	255 285		159		128		253	
500	20"		156	10K	144				154	¥0 142		283	6.0		
600	24"		208		190				405		206		188		403
700	28"		304		282		400		302		280		398		
-	30"		-		333		460		-		331		458		
800	32"		357		-		550		355		-		548		
900	36"		485		-		800		483		-		798		
1000	40"	PN 6	589		-		900	PN 6	587		-		898		
-	42"		-		-		1100		-		-		1098		
1200	48"		850		-	Д	1400		848		-	Д	1398		
-	54"		-		-	Class	2200		-		-	Class	2198		
1400	-		1300		-		-		1298		-	0	-		
-	60"		-		-		2700		-		-		2698		
1600	-		1700		-		_		1698		-		-		
-	66"		-		-		3700	-		-		3698			
1800	72"		2200		-		4100		2198		-		4098		
-	78"		-		-		4600		-		-		4598		
2000	_		2800		-		-		2798		-		-		

¹⁾ For flanges to AS, only DN 80, 100, 150 to 400, 500 and 600 are available.

Transmitter (compact version): 3.4 kg
 Weight data valid for standard pressure ratings and without packaging material.

Weight in US units (only ASME / AWWA)

Weight data in lbs									
Nominal diameter		Compact version			Remote version (without cable)				
				Sensor	Transmitter				
[mm]	[inch]		ASME /AWWA		ASME / AWWA	Wall-mount housing			
25	1"		16.1		11.7				
40	1½"		20.7		16.3				
50	2"		23.4		19.0				
80	3"		30.9		26.5				
100	4"		35.3		30.9				
150	6"		56.2		51.8				
200	8"	Class 150	99.2	Class 150	94.8				
250	10"	Class	165.4		161.0				
300	12"		242.6		238.1				
350	14"		385.9		381.5				
400	16"		452.0		447.6				
450	18"		562.3		557.9				
500	20"		628.4		624.0	13.2			
600	24"		893.0		888.6	13.2			
700	28"		882.0		877.6				
-	30"		1014.3		1009.9				
800	32"		1212.8		1208.3				
900	36"		1764.0		1759.6				
1000	40"		1984.5		1980.1				
-	42"	Class D	2425.5	Class D	2421.1				
1200	48"	Clas	3087.0	Clas	3082.6				
-	54"		4851.0		4846.6				
_	60"		5953.5		5949.1				
_	66"		8158.5		8154.1				
1800	72"		9040.5		9036.1				
_	78"		10143.0		10138.6				

Transmitter (compact version): 7.5 lbs
 Weight data valid for standard pressure ratings and without packaging material.

Measuring tube specifications

Dian	neter	Pressure rating						Internal diameter			
		EN (DIN)	AS 2129	AS 4087	ASME	AWWA	JIS	Hard 1	rubber	Polyur	ethane
[mm]	[inch]	[bar]			[lbs]			[mm]	[inch]	[mm]	[inch]
25	1"	PN 40	-	-	Cl. 150	-	20 K	-	-	24	0.94
32	-	PN 40	_	_	-	_	20 K	-	_	32	1.26
40	1½"	PN 40	-	-	Cl. 150	-	20 K	-	-	38	1.50
50	2"	PN 40	Table E	PN 16	Cl. 150	-	10 K	50	1.97	50	1.97
65	-	PN 16	-	-	1	-	10 K	66	2.60	66	2.60
80	3"	PN 16	Table E	PN 16	Cl. 150	-	10 K	79	3.11	79	3.11
100	4"	PN 16	Table E	PN 16	Cl. 150	-	10 K	102	4.02	102	4.02
125	-	PN 16	-	-	-	-	10 K	127	5.00	127	5.00
150	6"	PN 16	Table E	PN 16	Cl. 150	-	10 K	156	6.14	156	6.14
200	8"	PN 10	Table E	PN 16	Cl. 150	_	10 K	204	8.03	204	8.03
250	10"	PN 10	Table E	PN 16	Cl. 150	_	10 K	258	10.2	258	10.2
300	12"	PN 10	Table E	PN 16	Cl. 150	-	10 K	309	12.2	309	12.2
350	14"	PN 6	Table E	PN 16	Cl. 150	_	10 K	342	13.5	342	13.5
375	15"	-	_	PN 16	-	_	-	392	15.4	_	_
400	16"	PN 6	Table E	PN 16	Cl. 150	_	10 K	392	15.4	392	15.4
450	18"	PN 6	-	_	Cl. 150	_	10 K	437	17.2	437	17.2
500	20"	PN 6	Table E	PN 16	Cl. 150	-	10 K	492	19.4	492	19.4
600	24"	PN 6	Table E	PN 16	Cl. 150	-	10 K	594	23.4	594	23.4
700	28"	PN 6	-	-	1	Class D	10 K	692	27.2	692	27.2
750	30"	-	-	-	1	Class D	10 K	742	29.2	742	29.2
800	32"	PN 6	-	-	-	Class D	-	794	31.3	794	31.3
900	36"	PN 6	-	-	1	Class D	1	891	35.1	891	35.1
1000	40"	PN 6	-	-	1	Class D	1	994	39.1	994	39.1
-	42"	-	-	-	1	Class D	1	1043	41.1	1043	41.1
1200	48"	PN 6	-	-	_	Class D	-	1197	47.1	1197	47.1
-	54"		-	-	-	Class D	-	1339	52.7	-	-
1400	-	PN 6	-	-	-	-	-	1402	55.2	-	-
-	60"	-	-	_	-	Class D	-	1492	58.7	_	_
1600	-	PN 6	-	-	-	-	-	1600	63.0	-	-
-	66"	-	-	-	-	Class D	-	1638	64.5	-	-
1800	72"	PN 6	-	-	-	Class D	-	1786	70.3	-	-
2000	78"	PN 6	-	_	-	Class D	-	1989	78.3	_	_

Material

- Transmitter housing
 - Compact housing: powder-coated die-cast aluminum
 - Wall-mount housing: powder-coated die-cast aluminum
- Sensor housing
 - DN 25 to 300 (1 to 12"): powder-coated die-cast aluminum
 - DN 350 to 2000 (14 to 78"): with protective lacquering
- Measuring tube
 - DN ≤ 300 (12"): stainless steel 1.4301 or 1.4306 (304L);
 (for flanges made of carbon steel with Al/Zn protective coating)
 - DN ≥ 350 (14"): stainless steel 1.4301 or 1.4306 (304L);
 (for flanges made of carbon steel with Al/Zn protective coating)
- Electrodes: 1.4435, Alloy C-22, Tantalum
- Flange
 - EN 1092-1 (DIN2501)
 - DN 25 to 3501:
 - Stainless-steel, 1.4571, F316L
 - Carbon steel, S235JRG2, S235JR+N, P250GH, P245GH, E250C, A105
 - DN 350 to 6001:
 - Stainless-steel, 1.4571, F316
 - Carbon steel, P245GH, S235JRG2, S235JR+N, A105, E250C
 - DN > 6001:
 - Stainless-steel, 1.4404, F316L
 - Carbon steel, P245GH, S235JRG2, S235JR+N, P250GH, E250C
 - ASME B16.5
 - DN 25 to 600
 - Stainless-steel, F316L similar to 1.4404
 - Carbon steel, A105
 - AWWA C207: Carbon steel, A105, Cl.70 A181, P265GH, S275JR, E250C
 - JIS B2220:
 - Carbon steel, A105, A350 LF2
 - Stainless steel, F316L

 $(DN \le 300 (12") \text{ with Al/Zn protective coating; } DN \ge 350 (14") \text{ with protective lacquering)}$

- AS 2129: Carbon steel, A105, P235GH, P265GH, S235JRG2
- AS 4087: Carbon steel, A105, P265GH, S275JR
- \blacksquare Seals: to DIN EN 1514-1 IBC form
- Ground disks: 1.4435 (316, 316L), Alloy C22, Titanium, Tantalum

10rder code "Design", option A "insertion length short"

Fitted electrodes

Measuring electrodes, reference electrodes and empty pipe detection electrodes:

- Standard available with 1.4435, Alloy C-22, tantalum
- Optional: exchangeable measuring electrodes made of 1.4435 (DN 350 to 2000 / 14 to 78")

Process connections

Flange connection:

- EN 1092-1 (DIN 2501), DN ≤ 300 (12") form A, DN ≥ 350 (14") form B
 (Dimensions to DIN 2501, DN 65 PN 16 and DN 600 (24") PN 16 exclusively to EN 1092-1)
- ASME B16.5
- AWWA C 207, Class D
- JIS B2220
- AS 2129 Table E
- AS 4087 PN 16

Surface roughness

- Electrodes
 - 1.4435, Alloy C-22, tantal: ≤ 0.3 to 0.5 μ m (≤ 11.8 to 19.7 μ in)

(All data refer to parts in contact with medium)

Operability

Local operation

Display elements

- Liquid crystal display: backlit, two lines (Promag 50) or four lines (Promag 53) with 16 characters per line
- Custom configurations for presenting different measured-value and status variables
- Totalizer
 - Promag 50: 2 totalizers
 - Promag 53: 3 totalizers

Operating elements

Unified operation concept for both types of transmitter:

Promag 50:

- Local operation via three keys (S, O, F)
- Quick Setup menus for straightforward commissioning

Promag 53:

- Local operation via three keys (S, O, F)
- Application-specific Quick Setup menus for straightforward commissioning

Language groups

Language groups available for operation in different countries:

Promag 50, Promag 53:

- Western Europe and America (WEA):
 English, German, Spanish, Italian, French, Dutch, Portuguese
- Eastern Europe and Scandinavia (EES):
 English, Russian, Polish, Norwegian, Finnish, Swedish, Czech
- South and east Asia (SEA):
 English, Japanese, Indonesian

Promag 53:

China (CN): English, Chinese

You can change the language group via the operating program "FieldCare".

Remote operation

- Promag 50: Remote control via HART, PROFIBUS DP/PA
- Promag 53: Remote control via HART, PROFIBUS DP/PA, Modbus RS485, FOUNDATION Fieldbus

Certificates and approvals

	Constitution of the consti
CE mark	The measuring system is in conformity with the statutory requirements of the EC Directives. Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
C-tick symbol	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".
Pressure measuring device approval	Measuring devices with a nominal diameter smaller than or equal to DN 25 correspond to Article 4 (3) of the EC Directive 2014/68/EU (Pressure Equipment Directive) and have been designed and manufactured according to good engineering practice. Where necessary (depending on the medium and process pressure), there are additional optional approvals to Category II/III for larger nominal diameters.
Ex approval	Information about currently available Ex versions (ATEX, IECEx, FM, CSA, NEPSI) can be supplied by your Endress+Hauser Sales Center on request. All explosion protection data are given in a separate documentation which is available upon request.
Other standards and guidelines	 EN 60529 Degrees of protection by housing (IP code) EN 61010 Protection Measures for Electrical Equipment for Measurement, Control, Regulation and Laboratory Procedures. IEC/EN 61326 "Emission in accordance with requirements for Class A". Electromagnetic compatibility (EMC requirements) NAMUR NE 21: Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment. NAMUR NE 43: Standardization of the signal level for the breakdown information of digital transmitters with analog output signal. NAMUR NE 53: Software of field devices and signal-processing devices with digital electronics. ANSI/ISA-S82.01 Safety Standard for Electrical and Electronic Test, Measuring, Controlling and related Equipment - General Requirements Pollution degree 2, Installation Category II. CAN/CSA-C22.2 No. 1010.1-92 Safety requirements for Electrical Equipment for Measurement and Control and Laboratory Use. Pollution degree 2, Installation Category II
FOUNDATION Fieldbus certification	The flow device has successfully passed all the test procedures carried out and is certified and registered by the Fieldbus Foundation. The device thus meets all the requirements of the following specifications: Certified to FOUNDATION Fieldbus Specification The device meets all the specifications of the FOUNDATION Fieldbus H1. Interoperability Test Kit (ITK), revision status 5.01 (device certification number: on request) The device can also be operated with certified devices of other manufacturers Physical Layer Conformance Test of the Fieldbus Foundation
Modbus RS485 certification	The measuring device meets all the requirements of the Modbus/TCP conformity test and has the "Modbus/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out and is certified by the "Modbus/TCP Conformance Test Laboratory" of the University of Michigan.
PROFIBUS DP/PA certification	The flow device has successfully passed all the test procedures carried out and is certified and registered by the PNO (PROFIBUS User Organisation). The device thus meets all the requirements of the following specifications:

Certified to PROFIBUS PA, profile version 3.0 (device certification number: on request)
 The device can also be operated with certified devices of other manufacturers (interoperability)

the following specifications:

Ordering information

Your Endress+Hauser service organization can provide detailed ordering information and information on the order codes on request.

Accessories

Various accessories, which can be ordered separately from Endress+Hauser, are available for the transmitter and the sensor. Your Endress+Hauser service organization can provide detailed information on the order codes in question.

Documentation

- Flow Measurement (FA005D/06)
- Operating Instructions Promag 50 (BA046D/06 and BA049D/06)
- Operating Instructions Promag 50 PROFIBUS PA (BA055D/06 and BA056D/06)
- Operating Instructions Promag 53 (BA047D/06 and BA048D/06)
- Operating Instructions Promag 53 FOUNDATION Fieldbus (BA051D/06 and BA052D/06)
- Operating Instructions Promag 53 Modbus RS485 (BA117D/06 and BA118D/06)
- Operating Instructions Promag 53 PROFIBUS DP/PA (BA053D/06 and BA054D/06)
- Supplementary documentation on Ex-ratings: ATEX, IECEx, FM, CSA, NEPSI

Registered trademarks

HART[©]

Registered trademark of the HART Communication Foundation, Austin, USA

PROFIBUS®

Registered trademark of the PROFIBUS Nutzerorganisation e.V., Karlsruhe, D

FOUNDATION™ Fieldbus

Registered trademark of the Fieldbus Foundation, Austin, USA

Modbus®

Registered trademark of the Modbus Organisation

HistoROM™, S-DAT®, T-DAT™, F-CHIP®, FieldCare®, Fieldcheck®, FieldXpert™, Applicator® Registered or registration-pending trademarks of the Endress+Hauser Flowtec Group



