# Technical Information Liquistation CSF34

Automatic stationary sampler for liquid media; integrated controller with up to four measuring channels and digital Memosens technology



#### **Applications**

Liquistation CSF34 is a stationary sampler designed for the fully automated removal, defined distribution, and temperature-controlled storage of liquid media. The standard product version has two 0/4 to 20 mA analog inputs, two binary inputs and two binary outputs. Thanks to the modular platform concept, the CSF34 can be quickly and easily modified to create a measuring station.

- Communal and industrial wastewater treatment plants
- Laboratories and water management offices
- Monitoring of liquid media in industrial processes

#### Your benefits

- All-purpose plastic ASA-PC housing material
- Two-door housing for reliable sample temperature regulation
- Cooling system with forced-air cooling and protective finish
- Swift menu guidance, navigator and large display
- Dual bottle trays for easy sample transportation
- Practice-oriented programs ranging from simple time programs to event programs
- Functionality can be extended by installing modular electronic components
- Integrated data logger for recording measured values
- Service interface for data transmission



# Table of contents

Function and system design	4	Relay outputs	22
Sampler Liquistation CSF34	4	Electrical specification	
Sampler with online measurement	5	•	
Mode of operation with a vacuum pump	6	Protocol-specific data	23
Mode of operation with a peristaltic pump	8	HART	
Sampling with a flow assembly	9	PROFIBUS DP	
Sample distribution	10	Modbus RS485	
Sample preservation	10	Modbus TCP	
Sampling control	11	Ethernet/IP	
1	12	Web server	
1 1 5 11 /	12	WED Server	24
Sampler housing	13		
		Power supply	25
Equipment architecture	14	Electrical connection	
	14	Supply voltage	
siot and port assignment	- 1	Cable entries	25
		Mains fuse	
Communication and data processing	15	Power consumption	
		Power failure	25
Dependability	16		
	16	Performance characteristics	26
Maintainability	16	Sampling methods	26
Safety	18	Dosing volume	26
		Dosing accuracy	26
Input	12	Repeatability	26
Types of input		Intake speed	26
Measured values		Suction height	26
vieasureu varues	10	Hose length	26
_		Temperature control	26
<u> </u>	19		
Measuring range		Installation	2.7
	19	Installation instructions	
Accuracy	19	Mounting conditions	
Binary input, passive	19	Environment	20
- 1	19	Environment	
Signal characteristics	19	Ambient temperature	
Accuracy	19	Storage temperature	29
		Degree of protection	
Analog input, passive/active	19	Electrical safety	
Span		Relative humidity	
-	19	Relative multifluity	29
		_	
Ondonal	10	Process	30
<u> </u>	19	Process temperature	30
- · · · · · · · · · · · · · · · · · · ·	19	Process characteristics	30
Communication		Process pressure	30
Output signal	19	Process connection	30
Current outputs, active		Mechanical construction	31
Span		Dimensions	31
Signal characteristic		Weight	32
Signal on alarm		Materials	33
Load			
*	21	Operability	34
Cable specification	71	Operating concept	
		Display	
		Local operation	

Remote operation	36
Certificates and approvals	37
Ordering information	38 38 38 38
Accessories	41


# Function and system design

#### Sampler Liquistation CSF34

A complete sampling unit comprises:


- Controller with display, soft keys and navigator
- Vacuum or peristaltic pump for sampling
- PE or glass sample bottles for sample preservation
- Sampling chamber temperature regulator (optional) for safe sample storage
- Suction line with suction head

**№** 1



Example of a Liquistation, version with vacuum pump

- Controller 2
- Window (optional)
- Dosing chamber door
- Suction line connection
- Sampling chamber door
- Sample bottles, e.g. 2 x 12 bottles, PE, 1 liter
- Bottle trays (depending on sample bottles selected)
- Distribution plate (depending on sample bottles selected)
- Distribution arm
- 10 Vacuum system, e.g. Dosing system with conductive sample sensor



**₽** 2 Example of a Liquistation, version with peristaltic pump

- Controller
- Window (optional)
- Dosing chamber door
- Suction line connection
- Sampling chamber door
- Sample bottles, e.g. 2 x 12 bottles, PE, 1 liter
- Bottle trays (depending on sample bottles selected)
- Distribution plate (depending on sample bottles selected)
- Distribution arm
- 10 Peristaltic pump

# Sampler with online measurement


i

The following overview shows examples of the design and layout of a measuring system. Other sensors and assemblies can be ordered for conditions specific to your application. See Accessories section and also --> www.endress.com/products

#### Measuring point


A complete measuring system with online measurement consists of:

- Liquistation CSF48 sampler
- Sensors with Memosens technology
- Immersion or flow assemblies to suit the sensors used



#### Nitrate

- Liquistation CSF48 sampler
- Sensors with Memosens technology
- Immersion or flow assemblies to suit the sensors used




#### Conductivity

Inductive conductivity measurement

- Flexdip CYA112 immersion assembly
- Indumax CLS50D sensor with fixed cable


Conductive conductivity measurement


- Flexdip CYA112 immersion assembly
- Condumax CLS15D sensor



#### Oxygen

- Flexdip CYA112 immersion assembly
- Flexdip CYH112 holder
- Sensor
  - Oxymax COS61D (optical) with fixed cable,
  - Oxymax COS51D (amperometric) cable CYK10






#### Turbidity

- Flexdip CYA112 immersion assembly
- Spray head CUR4 (optional)
- Turbimax CUS51D sensor with fixed cable




#### pH value or ORP

- Retractable assembly Cleanfit CPA471
- Orbisint CPS11D, CPS12D sensor
- Measuring cable CYK10




- Flowfit CUA250 flow assembly
- Turbimax CUS51D sensor with fixed cable




 Flexdip CYA112 immersion assembly

- Orbisint CPS12D, CPS11D sensor
- Measuring cable CYK10



# Mode of operation with a vacuum pump

#### Sampling takes place in four steps:



1. Blow clear

The vacuum pump blows the suction line clear via the dosing system.

#### 2. Intake

The "Airmanager" (pneumatic control unit) switches the air path of the vacuum pump to "intake". The sample is drawn into the dosing beaker until it reaches the conductivity probes of the dosing system.


#### 3. Dose

The intake process ends. Depending on the position of the dosing tube (item D), the excess sample liquid flows back to the sampling point.

#### 4. Drain

→ The hose clamp is opened and the sample is drained into the sample bottle.

#### Dosing system with conductive sample sensor



A002266


#### ■ 3 Conductive dosing system

- 1 Conductivity sensor 1 (common electrode)
- 2 Conductivity sensor 2 (safety electrode)
- 3 Conductivity sensor 3 (standard electrode)
- 4 Insulation
- 5 Measuring jug (plastic version with graduated scale or glass)
- 6 Graduated dosing tube, white and blue scale

#### Sample detection principle

When the sample is drawn in, the sample level reaches conductivity sensors 1 and 3. The system thus detects that the measuring jug is filled and terminates the suction process. If sensor 3 is heavily fouled or fails, conductivity sensor 2 switches to safety mode and turns off the system. This patented sample detection method along with predictive maintenance information prevent vacuum pump failure as a result of flooding.

#### Dosing system with capacitance sample sensor



#### 

- 1 Hose connection for the vacuum pump
- 2 Graduated measuring jug
- 3 Graduated dosing tube, white and blue scale
- 4 Capacitance level sensor

#### Sample detection principle

When the level of medium in the measuring jug changes, the capacitance of a capacitor partly formed by the liquid also changes..


The capacitance sensor ensures rapid sample detection in media that form foam and have a high fat content, and media with a conductivity  $< 30~\mu S/cm$ . Only capacitance level detection is possible in the latter type of media.

# i

#### Sample dosing with/without pressure

Sample dosing without pressure is the factory setting for all standard applications in which the sample medium is taken from an open channel or a gravity line. The excess sample can flow back under atmospheric pressure. Sample dosing with pressure is selected for applications in which the sample is taken from a pipe, for example, or for applications involving a low suction height and a low sample volume. In such instances, the sample medium cannot flow back on its own. The maximum pressure in the pipe must be < 0.8 bar. Pressure is applied and the excess sample is forced out of the measuring jug and back to the sampling point. The sample volume is set by adjusting the dosing tube. The white "A" scale applies if dosing without pressure, and the blue "B" scale applies if dosing with pressure.

# Mode of operation with a peristaltic pump




**■** 5 Sampling steps with a peristaltic pump

#### Sampling takes place in three steps:

- 1. Rinse
  - └ The peristaltic pump runs in reverse and forces medium back to the sampling point.
- 2. Intake
  - The peristaltic pump runs forward and draws in medium. If the medium detection system detects the sample, the pump is controlled by the flow and the specified sample volume is calculated automatically.
- 3. Drain
  - The pump runs in reverse again and forces the medium back to the sampling point.

One advantage this system offers for obtaining a representative sample is the possibility of rinsing the suction line several times: Medium is initially drawn in until the medium detection system reacts, then the pump switches and forces the medium back to the sampling point. This process can be repeated a maximum of three times. The sample is then taken as described.



■ 6 Peristaltic pump

- 1 Pump tube
- 2 Safety switch (optional)
- 3 Pump rollers
- 4 Medium detection system (patented)

The pump rollers deform the hose, thereby causing a negative pressure and the suction effect. The medium detection system is based on a pressure sensor which detects the difference between a pipe that is filled and not filled. Thanks to a patented process for automatically detecting the suction height, the user does not have to enter the suction height or suction line length. The self-learning software guarantees that the sample volume remains constant. An optional safety switch integrated in the pump housing immediately switches off the pump when the pump is opened (recommended if third-party staff are performing maintenance work).

8 Endress+Hauser

A002434

# Sampling with a flow assembly

A flow assembly is integrated in the stand for sampling purposes.

The flow assembly is used for sampling in pressurized systems e.g.:

- Tanks positioned at a height
- Pressure piping
- Conveyance using external pumps


The flow rate should be 1000 to 1500 l/h.

#### NOTICE

#### Pressure in the assembly

Damage to the assembly

► The outlet of the flow assembly must be unpressurized (e.g. drain, open channel).




A002434

- 7 Example: Sampling from pressure piping
- 1 Ball valve 1
- 2 Valve 2
- 3 Flow assembly integrated into the stand

Use the ball valve 1 to set the flow rate to 1000 l/h to 1500 l/h. When the sampling cycle begins, one of the relay outputs can be used to control and open valve 2. The medium flows through the pipe and the flow assembly and into the outflow. Once an adjustable delay time has elapsed, the sample is taken directly from the flow assembly. Valve 2 is closed again once the sample has been taken.

Yalve 1 and valve 2 are not included in the scope of delivery (order code TSP 71180379).



■ 8 Flow assembly (can also be ordered separately as kit no.: 71119408)

Flow assembly inflow: ¾"
Sampling connection
Flow assembly outflow: 1¼"

A001312

#### Sample distribution

The CSF34 offers many bottle combinations and distribution versions. The versions can be changed or replaced easily without the need for special tools. In addition, the software program makes it possible to configure individual bottles and bottle groups and assign them to switchover or event programs.

#### Sample preservation

The sample bottles are located in the sample compartment. This is fitted with a seamless plastic dish to ensure easy cleaning. All parts that transport medium (distribution arm, dosing system...) can be removed and cleaned easily without the need for tools.




A0029681

Bottle groups and distribution version depending on the order version:

	В	С	D	E	I	F	G	Н
30 liter, PE, direct distribution								
A0024349	1							
60 liter, PE, direct distribution		1						
A0025843								
25 liter, PE, direct distribution			2					
A0024349								
13 liter, PE, direct distribution				4				
A0025968								

	В	С	D	E	I	F	G	Н
3.8 liter, glass, direct distribution					4			
A0025970								
2 liter, PE, direct distribution						12		6
A0025976								
1 liter, PE, direct distribution							24	12
A0025978								

#### Sampling control



- a. Flow curve
- Time-proportional sampling (CTCV)
   A constant sample volume (e.g. 50 ml) is taken at regular intervals (e.g. every 5 minutes).
- Volume-proportional sampling (VTCV)
   A constant sample volume is taken at variable intervals (depending on the inflow volume).
  - Time override can be enabled in an advanced program. This allows long, flow-controlled sample intervals to be interrupted if the flow rate is low. A time-controlled sample is collected.
- d. Flow-proportional sampling (CTVV)


A variable sample volume (the sample volume depends on the flow rate) is taken at regular intervals (e.g. every 10 min).

- lacktriangle Only in version with peristaltic pump.
- . Event-controlled sampling

Sampling is triggered by an event (e.g. pH limit value). Sampling can be time-paced, volume-paced or flow-paced, or single samples can be taken.

Single and multiple samples can also be grouped in a program in addition to the sampling methods listed. Furthermore, the software allows interval sampling, switchover and event functions. The latter permit up to 24 subprograms to be active simultaneously for a variety of applications. A sampling table makes it possible for users to program the bottle assignment, time interval and sample volume. Signals for external control can be connected via 2 analog inputs and 2 binary inputs in the standard version of the product. Customized text is entered to ensure the correct assignment of the inputs in the memory.

# Intake speed with different suction lines



■ 10 Intake speed in m/s with suction height in m

- a Intake speed as per Ö 5893; US EPA
- b Intake speed as per EN 25667, ISO 5667
- 1 ID 10 mm (3/8") vacuum pump
- 2 ID 13 mm (1/2") vacuum pump
- 3 ID 10 mm (3/8") peristaltic pump
- 4 ID 16 mm (5/8") vacuum pump
- 5 ID 19 mm (3/4") vacuum pump

# Sample temperature regulation (optional)

The standard cooling system is located in the upper rear section. Any exposed copper materials are coated to protected against corrosion.

The temperature of the sample compartment can be adjusted using the controller. The factory setting is  $4 \,^{\circ}\text{C}$  (39  $^{\circ}\text{F}$ ). The current temperature is shown on the display and can be recorded in the internal data logger.

A temperature sensor for measuring individual sample temperatures can be ordered as an option.

The vaporizer and defrost heater are integrated in a special housing such that they are protected against corrosion and damage. The compressor and condenser are located in the upper section of the sampler. They can be easily accessed by removing the upper rear panel (for maintenance purposes).



■ 11 Cooling system

A0024355

#### Sampler housing

Pay attention to the installation conditions in the "Installation" section and the information on the materials of the different housing types in the "Mechanical construction" section.

#### **NOTICE**


#### The plastic material polystyrene VO can discolor if exposed directly to sunlight.

In the case of stainless steel housings, the frame around the window can discolor if exposed directly to sunlight.

► The plastic material ASA+PC VO is recommended for outdoor installations where a sun guard is not used. The discoloring does not affect the function and operation of the device.

### **Equipment architecture**

#### Slot and port assignment



 $\blacksquare$  12 Slot and port assignment of hardware and presentation on the display

#### The electronics configuration follows a modular concept:

- There are several slots for electronics modules.
- These slots are numbered consecutively in the housing. Slots 0 and 1 are always reserved for the basic module.
- In addition there are also inputs and outputs for the control module. These slots are labeled "S".
- Each electronics module has one or more inputs and outputs or relays. Here they are all collectively known as "ports".
- Ports are consecutively numbered per electronics module and are recognized automatically by the software.
- Outputs and relays are named according to their function, e.g. "current output", and are displayed in ascending order with the slot and port numbers.
   Example:
  - "Current output 2:1" shown on the display means: slot 2 (e.g. AOR module): port 1 (current output 1 of the AOR module)
- Inputs are assigned to measuring channels in the ascending order of "slot:port number" Example:
  - "CH1: 1:1" shown on the display means:
  - Slot 1 (base module) : port 1 (input 1) is channel 1 (CH1) and a conductivity sensor is connected here.

# Communication and data processing

#### **Communication protocols:**

- Fieldbus systems
  - HART
  - PROFIBUS DP (Profile 3.02)
  - Modbus TCP or RS485
  - PROFINET
  - Ethernet/IP
- Configuration via Ethernet
- Only one type of fieldbus communication can ever be active. The last activation code entered decides which bus is used.

The device drivers available make it possible to perform a basic setup and display measured values and diagnostics information via the fieldbus. A full device configuration via the fieldbus is not possible.

#### Bus termination on the device

- Via slide switch at bus module 485
- Displayed via LED "T" on bus module 485

### **Dependability**

#### Reliability

#### Memosens technology

#### MEMO() SENS

Memosens makes your measuring point safer and more reliable:

- Non-contact, digital signal transmission enables optimum galvanic isolation
- No contact corrosion
- Completely watertight
- Laboratory sensor calibration possible, thus increasing measured value availability
- Predictive maintenance thanks to recording of sensor data, e.g.:
  - Total hours of operation
  - Hours of operation with very high or very low measured values
  - Hours of operation at high temperatures
  - Number of steam sterilizations
  - Sensor condition



A002435

#### Sensor check system (SCS)

The sensor check system (SCS) monitors the high impedance of the pH glass. An alarm is triggered if a minimum impedance value is undershot or a maximum impedance is exceeded.

- Glass breakage is the main reason for a drop in high impedance values.
- The causes of increasing impedance values are:
  - Dry sensor
  - Worn pH glass membrane

#### Process check system (PCS)

The process check system (PCS) checks the measuring signal for stagnation. An alarm is triggered if the measuring signal does not change over a certain period (several measured values).

#### The main causes of stagnating measured values are:

- Sensor fouled or outside the medium
- Sensor defective
- Process error (e.g. through control system)

#### Sensor condition check (SCC)

This function monitors the electrode condition and the degree of electrode aging. The status is indicated by the messages "SCC electrode condition bad" or "SCC electrode condition OK". The electrode condition is updated after every calibration.

#### Maintainability

#### Modular design

The modular sampler design means it can be easily adapted to suit your needs:


- Retrofit extension modules for new or extended range of functions, e.g. current outputs and relays
- Upgrade from one channel to multichannel measurement with digital sensors
- Upgrade to fieldbus communication (PROFIBUS DP, Modbus TCP, Modbus RS485, Ethernet, PROFINET for configuration and EtherNet/IP)

#### Memory

- Independent, integrated ring memories (FIFO) or stack memories for recording:
  - An analog value (e.g. flow, pH value, conductivity)
  - Events (e.g. power failure)
  - Sample statistics (e.g. sampling volume, filling times, bottle assignment)
- Program memory: max. 100 programs
- Data logbooks:
  - Adjustable scan time: 1 to 3600 s (1 h)
  - Max. 8 data logbooks
  - 150,000 entries per logbook
  - Graphic display (load curves) or numerical list
- Calibration logbook: max. 75 entries

16

- Hardware logbook:
  - Hardware configuration and modifications
  - Max. 125 entries
- Version logbook:
  - Including software updates
  - Max. 50 entries
- Operations logbook: max. 250 entries
- Diagnostic logbook: max. 250 entries



■ 13 Data logbook: graphic display

FieldCare and Field Data Manager

### FieldCare

Configuration and asset management software based on FDT/DTM technology

- Complete device configuration when connected via FXA291 and service interface
- Access to a number of configuration parameters and identification, measuring and diagnostic data when connected via HART modem
- Logbooks can be downloaded in CSV format or binary format for "Field Data Manager" software


#### Field Data Manager

Visualization software and database for measuring, calibration and configuration data

- SQL database which is protected against manipulation
- Functions to import, save and print out logbooks
- Load curves to display measured values
- All the logbooks can be read out and saved online

Endress+Hauser 17

A0024359



■ 14 Field Data Manager: load curves

A0016009

#### SD card

The exchangeable storage medium enables:

- Quick and easy software updates and upgrades
- Data storage of internal device memory (e.g. logbooks)
- Transfer of complete configurations to a device with an identical setup (backup function)
- Transfer of configurations without the TAG and bus address to devices with an identical setup (copy function)

Endress+Hauser offers industry-approved SD cards as accessories. These memory cards provide maximum data security and integrity.

Other SD cards can also be used. However, Endress+Hauser does not accept any responsibility for the data security of such cards.

#### Safety

#### Real-time clock

The device has a real-time clock, which is backed up by a button cell in the event of a power failure. This ensures that the device continues to keep the correct time and date if it is restarted and that the time stamp for the logbooks is correct.

#### Data security

All settings, logbooks etc. are stored in a non-volatile memory to ensure that the data are retained even in the event of a disruption to the power supply.

# Input

#### Types of input

- 2 analog inputs
- 2 binary inputs + 2 binary inputs (optional)
- 1 to 4 digital inputs for sensors with Memosens protocol (optional)

#### Measured values

→ Documentation of the connected sensor

18

### **Temperature inputs**

Measuring range	<b>Measuring range</b> -30 to 70 °C (-20 to 160 °F)
Type of input	Pt1000
Accuracy	± 0.5 K

### Binary input, passive

Span	12 to 30 V, galvanically isolated	
Signal characteristics	Minimum pulse width: 100 ms	
Accuracy	± 0.5 K	

# Analog input, passive/active

Span	0/4 to 20 mA, galvanically isolated
Accuracy	±0.5 % of measuring range

# Output

#### Output signal

- 2 binary outputs (standard) + 2 binary outputs (optional):
   Open collector, max. 30 V, 200 mA
- Up to  $2 \times 0/4$  to 20 mA, active, galvanically isolated from the sensor circuits and from each other  $2 \text{ to } 6 \times 0/4$  to 20 mA, active, galvanically isolated from the sensor circuits and from each other
- Of those, 1 x with optional HART communication (only via current output 1:1). Limited to 2 current outputs with optional fieldbus communication.

#### Communication

- 1 service interface
- Accessible via front panel connection (optional)
- Commubox FXA291 (accessory) required for communication with the PC

#### Output signal

#### Depending on version:

- 2 x 0/4 to 20 mA, active, galvanically isolated from one another and from the sensor circuits
- $\,\blacksquare\,$  4 x 0/4 to 20 mA, active, galvanically isolated from one another and from the sensor circuits
- 6 x 0/4 to 20 mA, active, galvanically isolated from one another and from the sensor circuits
- $\bullet$  8 x 0/4 to 20 mA, active, galvanically isolated from one another and from the sensor circuits
- Optional HART communication (only via current output 1:1)

HART				
Signal encoding	FSK ± 0.5 mA via current signal			
Data transmission rate	1200 baud			
Galvanic isolation	Yes			
Load (communication resistor)	250 Ω			

PROFIBUS DP/RS485	
Signal encoding	EIA/TIA-485, PROFIBUS DP-compliant acc. to IEC 61158
Data transmission rate	9.6 kBd, 19.2 kBd, 45.45kBd, 93.75 kBd, 187.5 kBd, 500 kBd, 1.5 MBd, 6 MBd, 12 MBd
Galvanic isolation	Yes
Connectors	Spring terminal (max. 1.5 mm), bridged internally (T-function), optional M12
Bus termination	Internal slide switch with LED display

Modbus RS485				
Signal encoding	EIA/TIA-485			
Data transmission rate	2,400, 4,800, 9,600, 19,200, 38,400, 57,600 and 115,200 baud			
Galvanic isolation	Yes			
Connectors	Spring terminal (max. 1.5 mm), bridged internally (T-function), optional M12			
Bus termination	Internal slide switch with LED display			

Ethernet and Modbus TCP				
Signal encoding	IEEE 802.3 (Ethernet)			
Data transmission rate	10/100 MBd			
Galvanic isolation	Yes			
Connection	RJ45			
IP address	DHCP (default) or configuration via menu			

Ethernet/IP				
Signal encoding	IEEE 802.3 (Ethernet)			
Data transmission rate	10/100 MBd			
Galvanic isolation	Yes			
Connection	RJ45			
IP address	DHCP (default) or configuration via menu			

PROFINET		
Signal encoding	IEEE 802.3 (Ethernet)	
Data transmission rate	100 MBd	
Galvanic isolation	Yes	
Connection	RJ45	
Name of station	Via DCP protocol using the configuration tool (e.g. Siemens PRONETA)	
IP address	Via DCP protocol using the configuration tool (e.g. Siemens PRONETA)	

# Current outputs, active

<u> </u>	0 . 22 . 4
Span	0 to 23 mA
	2.4 to 23 mA for HART communication
Signal characteristic	Linear
Signal on alarm	Adjustable, as per NAMUR Recommendation NE 43 <ul> <li>In measuring range 0 to 20 mA (HART is not available with this measuring range): Failure current from 0 to 23 mA</li> <li>In measuring range 4 to 20 mA: Failure current from 2.4 to 23 mA</li> </ul>
 Load	• Factory setting for failure current for both measuring ranges: 21.5 mA $$\rm Max.500\Omega$$
Electrical specification	Output voltage
	Max. 24 V
Cable specification	Cable type
	Recommended: shielded cable
	Cross-section Cross-section
	Recommended: shielded cable

# Relay outputs

#### **Electrical specification**

#### Relay types

- 2 x changeover contact, coupled with binary output (optional)
   1 single-pin changeover contact (alarm relay)
- 1 relay card with 2 or 4 relays (optional)

#### Maximum load

 Alarm relay: 0.5 A ■ All other relays: 2.0 A

#### Relay switching capacity

#### Power unit (Alarm relay)

Switching voltage	Load (max.)	Switching cycles (min.)
230  V AC, cosΦ = 0.8 to 1	0.1 A	700,000
	0.5 A	450,000
24 V DC, L/R = 0 to 1 ms	0.1 A	500,000
	0.5 A	350,000

#### Relay coupled with binary output

Switching voltage	Load (max.)	Switching cycles (min.)
230 V AC, $cosΦ = 0.8$ to 1	5 A	100,000
24 V DC, L/R = 0 to 1 ms	5 A	100,000

#### Extension module

Switching voltage	Load (max.)	Switching cycles (min.)	
230 V AC, cosΦ = 0.8 to 1	0.1 A	700,000	-
	2 A	120,000	-
		0.1 A	1,000,000
2 A	to 1	170,000	
24 V DC, L/R = 0 to 1 ms		0.1 A	500,000
	2 A	150,000	

#### Minimum load (typical)

- Min. 100 mA at 5 V DC
- Min. 1 mA at 24 V DC
- Min. 5 mA at 24 V AC
- Min. 1 mA at 230 V AC

### Protocol-specific data

	Protocol-specific data	l
HART	Manufacturer ID	11 <sub>h</sub>
	Device type	119D <sub>h</sub>
	Device revision	001 <sub>h</sub>
	Device description files (DD/DTM)	www.endress.com/hart Device Integration Manager DIM
	Device variables	
	Supported features	PDM DD, AMS DD, DTM,
PROFIBUS DP	Manufacturer ID	11 <sub>h</sub>
	Device type	155C <sub>h</sub>
	Profile version	3.02
	GSD files	
	GSD files	www.endress.com/profibus Device Integration Manager DIM
	Output values	
	Supported features	<ul> <li>1 MSCYO connection (cyclical communication, master class 1 to slave)</li> <li>1 MSAC1 connection (acyclical communication, master class 1 to slave)</li> <li>2 MSAC2 connections (acyclical communication, master class 2 to slave)</li> <li>Addressing using DIL switches or software</li> <li>GSD, PDM DD, DTM</li> </ul>
Modbus RS485	Protocol	RTU/ASCII
	Function codes	03, 04, 06, 08, 16, 23
	Broadcast support for function codes	06, 16, 23
	Output data	16 measured values (value, unit, status), 8 digital values (value, status)
	Input data	4 setpoints (value, unit, status), 8 digital values (value, status), diagnostic information
	Supported features	Address can be configured using switch or software
Modbus TCP	TCP port	502
	TCP connections	3
	Protocol	TCP
	Function codes	03, 04, 06, 08, 16, 23
	Broadcast support for function codes	06, 16, 23
	Output data	16 measured values (value, unit, status), 8 digital values (value, status)
	Input data	4 setpoints (value, unit, status), 8 digital values (value, status),

Endress+Hauser 23

Supported features

diagnostic information

Address can be configured using DHCP or software

#### Ethernet/IP

Log	EtherNet/IP	
ODVA certification	Yes	
Device profile	Generic device (p	roduct type: 0x2B)
Manufacturer ID	0x049E <sub>h</sub>	
Device type ID	0x109	
Polarity	Auto-MIDI-X	
Connections	CIP	12
	I/O	6
	Explicit message	6
	Multicast	3 consumers
Minimum RPI	100 ms (default)	
Maximum RPI	10000 ms	
System integration	EtherNet/IP	EDS
	Rockwell	Add-on-Profile Level 3, Faceplate for Factory Talk SE
IO data	Input $(T \rightarrow O)$	Device status and diagnostic message with highest priority
		Measured values:  16 AI (analog input) + Status + Unit  8 DI (discrete input) + Status
	Output (O → T)	Actuating values:  4 A0 (analog output) + status + unit  8 D0 (discrete output) + Status

#### Web server

The Web server enables full access to the device configuration, measured values, diagnostic messages, logbooks and service data via standard WiFi/WLAN/LAN/GSM or 3G routers with a user-defined IP address.

TCP port	80
Supported features	<ul> <li>Remote-controlled device configuration</li> <li>Save/restore device configuration (via SD card)</li> <li>Logbook export (file formats: CSV, FDM)</li> <li>Access to Web server via DTM or Internet Explorer</li> </ul>

# Power supply

Electrical connection	> For a detailed connection plan, see the Operating Instructions for Liquistation CSF34
Supply voltage	Depending on version: 100 to 120/200 to 240 V AC $\pm 10$ %, 50/60 Hz
	The device does not have a power switch.
	A fuse with a maximum rating of 10 A must be provided by the customer. Observe the local regulations for installation.
Cable entries	Depending on version: ■ 1 x M25, 7 x M20 cable gland ■ 1 x M25, 1 x M20 cable gland
	Permitted cable diameter:  M20x1.5 mm: 7 to 13 mm (0.28 to 0.51")  M25x1.5 mm: 9 to 17 mm (0.20 to 0.67")
Mains fuse	<ul> <li>T3.15A (for 230V power supply)</li> <li>T10A (for 24V power supply)</li> <li>T10A (fuse for battery backup)</li> </ul>
Power consumption	<ul> <li>Version with vacuum pump: 290 VA</li> <li>Version with peristaltic pump: 290 VA</li> <li>Version with sampling assembly: 290 VA</li> <li>Version with 24V power supply: 240 W</li> </ul>
Power failure	Power supply (optional): 2 x 12 V, 7.2 Ah, with additional charge controller
	Replace the rechargeable batteries with type Panasonic LC-R127R2PG1.
	Real-time clock: lithium battery, type CR2032

### Performance characteristics

# Sampling methods

#### Vacuum pump/peristaltic pump/sampling assembly:

- Event sampling
- Single and multiple samples
- Sampling table

#### Vacuum pump:

- Time-paced
- In proportion to volume

#### Peristaltic pump:

- Time-paced
- In proportion to volume
- Flow proportional sampling/time override (CTVV)

#### Dosing volume

#### Vacuum pump:

20 to 350 ml (0.7 to 12 fl.oz.)

#### Peristaltic pump:

10 to 10000 ml (0.3 to 340 fl.oz.)



The dosing accuracy and the repeatability of a sample volume < 20 ml can vary, depending on the specific application.

#### Dosing accuracy

- Vacuum pump:
  - $\pm$  5 ml (0.17 fl.oz.) or 5 % of the set volume
- Peristaltic pump:

 $\pm$  5 ml (0.17 fl.oz.) or 5 % of the set volume

#### Repeatability

5 %

### Intake speed

> 0.5 m/s (> 1.6 ft/s) for  $\le 13$  mm (1/2") ID, as per EN 25667, ISO 5667, CEN 16479-1

> 0.6 m/s (> 1.9 ft/s) for 10 mm (3/8") ID, in accordance with Ö 5893; US EPA

#### Suction height

#### Vacuum pump:

Max. 6 m (20 ft) or max. 8 m (26 ft), depending on the version

### Peristaltic pump:

Max. 8 m (26 ft)

### Hose length

Max. 30 m (98 ft)

#### Temperature control

#### Temperature sensors:


- Sampling compartment temperature
- Sample temperature (optional)
- Outside temperature (optional)

#### Cooling module:

- Sample temperature range: 2 to 20 °C (36 to 68 °F)
   Factory setting: 4 °C (39 °F)
- Automatic defrost system
- Cooling rate in accordance with Ö 5893 (Austrian standard):
   4 liters of water at 20 °C cool down to 4 °C in less than 210 minutes
- $\blacksquare$  Temperature constancy of sample at 4 °C over the operating temperature range of -15 to 40 °C (5 to 105 °F)


### Installation

#### **Installation instructions**



- **■** 15 Foundation plan
- Fasteners (4 x M10)
- Cable inlet
- Outlet for condensate and overflow > DN 50 С
- Sample supply from below > DN 80 Dimensions of Liquistation D

#### Mounting conditions



Liquistation mounting conditions

- 1. Correct
  - The suction line must be routed with a downward slope to the sampling point.
- - The sampler should never be mounted in a place where it is exposed to aggressive gases.

- 3. Incorrect
  - ► Avoid siphoning effects in the suction line.
- 4. Incorrect
  - └ The suction pipe should never be routed with an upward gradient to the sampling point.

Note the following when erecting the device:

- Erect the device on a level surface.
- Securely connect the device at the fastening points to the surface underneath.
- Protect the device against additional heating (e.g. heater or direct sunlight in the case of PS housing).
- Protect the device against mechanical vibrations.
- Protect the device against strong magnetic fields.
- Make sure air can circulate freely at the side panels of the cabinet. Do not mount the device
  directly against a wall. Allow at least 150 mm (5.9") from the wall to the left and right.
- Do not erect the device directly above the inlet channel of a wastewater treatment plant.

# **Environment**

Ambient temperature	-30 to 50 °C (-20 to 120 °F)	
Storage temperature	−20 to 60 °C (−4 to 140 °F)	
Degree of protection	<ul> <li>Front dosing compartment: IP 54</li> <li>Rear dosing compartment: IP 33</li> <li>Front panel with display (internal): IP 65</li> <li>Sample compartment: IP 54</li> </ul>	
Electromagnetic compatibility	Interference emission and interference immunity as per EN 61326-1:2006, class A for industry	
Electrical safety  In accordance with EN 61010-1, protection class I, environment ≤ 2000 m (6500 ft) about device is designed for pollution degree 2.		
Relative humidity	10 to 95%, not condensing	

### **Process**

#### **Process temperature**

2 to 50 °C (36 to 122 °F)

#### **Process characteristics**

#### Vacuum pump

Capacitance level measurement used for:

- Sample media has to be free of abrasive substances.
- Media that tend to create a lot of foam or contain fats and grease
- Media with a conductivity < 30 µS/cm

#### Peristaltic pump

Sample media has to be free of abrasive substances.



Pay attention to the material compatibility of the wetted parts.

#### **Process pressure**

- Unpressurized, open channel (unpressurized sampling)
- Max. 0.8 bar piping (only with shutoff/inlet valve)

#### Sampling assembly:

Max. 6 bar

#### **Process connection**

#### Vacuum pump:

Suction line ID 10 mm (3/8"), 13 mm (1/2"), 16 mm (5/8") or 19 mm (3/4")


Peristaltic pump:

Intake hose ID 10 mm (3/8")

- Sampling assembly:
  - Flange DN50, PP
  - Triclamp DN50, DIN 32676


# Mechanical construction

#### Dimensions



■ 17 Dimensions of Liquistation CSF34 plastic version, without/with stand, dimensions in mm (in)

A Suction line connection



■ 18 Dimensions of Liquistation CSF34 stainless steel version, without/with stand, dimensions in mm (in)

#### A Suction line connection

#### Weight

	Sampler version	Weight	
Plastic version with refrigeration		101 kg (223 lbs)	

32

#### Materials

Plastic polystyrene VO can change color when exposed to direct sunlight. For outdoor use without a weather protection cover, the use of Plastic ASA+PC V0 is recommended. The functionality is not affected by the discoloration.

Non-wetted parts	
Cabinet housing	Plastic ASA+PC V0 For industrial wastewater treatment plants with an aggressive atmosphere
Sample compartment inner lining	Plastic PP
Window	Safety glass, coated
Insulation	Plastic EPS "Neopor®"

Choose process seal depending on the application. Viton is recommended for standard applications involving watery samples.

Vacuum pump only	
Pneumatic hoses	Silicone
Air Manager housing	PC
Air Manager sealing plate	Silicone
Pump head	Aluminum, anodized
Pump membrane	EPDM


### Operability

#### Operating concept

The simple and structured operating concept sets new standards:

- Intuitive operation with the navigator and soft keys
- Fast configuration of application-specific measurement options
- Easy configuration and diagnosis thanks to plain-text display
- All languages that can be ordered are available in every device





A0024560

MODE

■ 19 Easy operation


Plain-text menu


MAN


#### Display

#### Graphic display:

- Resolution: 240 x 160 pixel
- Back light with switch-off function
- Red display background for alarms alerts users to errors
- Transflective display technology for maximum contrast even in bright environments
- User-definable measuring menus mean you can always keep track of the values that are important for your application.







Example of measuring menu

#### Local operation




- LCD, illuminated (with red background in the event of an error)
- 160 x 240 pixels
- 4 operating keys (soft key function) and navigator (jog/shuttle and press/hold function)
- Menu-guided operation

A0024469

#### Remote operation


#### Via HART (e.g. via HART modem and FieldCare)



#### HART using modem

- Device module Base2-E: current output 1 with HART
- HART modem for connection to PC, e.g. Commubox FXA191 (RS232) or FXA195  $^{1)}$  (USB)
- HART handheld terminal
- 1) Switch position "on" (substitutes the resistor)


#### Via PROFIBUS DP



■ 24 PROFIBUS DP

Terminating resistor


#### Via Modbus RS485



■ 25 Modbus RS485

T Terminating resistor

#### Via Ethernet: web server/Modbus TCP/PROFINET/EtherNet/IP



■ 26 Modbus TCP or EtherNet/IP or PROFINET

#### Communication

- 1 service interface
- Optionally on front panel
- Commubox FXA291 (accessory) required for communication with the PC

#### Software

#### Field Data Manager

- Standardized user interface under Windows®
- Read-out of internal memory containing the measured flow rate, sample volume taken etc.

#### FieldCare

- Device settings saved in a database
- Configuration

36

# Certificates and approvals

# C€ mark **Declaration of Conformity** The product meets the requirements of the harmonized European standards. As such, it complies with the legal specifications of the EU directives. The manufacturer confirms successful testing of the product by affixing to it the **C€** mark. Approvals for power supply The power supply is approved by:

- CSA ("C" and "US")
- UL (UL 60950-1) ("C" and "US")
- UL (UL 508)

# **Ordering information**

## Product page

#### www.endress.com/CSF34

# **Product Configurator**

On the product page there is a **Configure** button to the right of the product image.

- 1. Click this button.
  - ► The Configurator opens in a separate window.
- 2. Select all the options to configure the device in line with your requirements.
  - In this way, you receive a valid and complete order code for the device.
- 3. Export the order code as a PDF or Excel file. To do so, click the appropriate button on the right above the selection window.
- For many products you also have the option of downloading CAD or 2D drawings of the selected product version. Click the **CAD** tab for this and select the desired file type using picklists.

## Scope of delivery

The scope of delivery comprises:

- 1 Liquistation CSF34 with:
  - The ordered bottle configuration
  - Optional hardware
- Accessories kit
  - .
- For peristaltic or vacuum pump: Connection nipple for suction line with various angles (straight, 90°), Allen key (for version with vacuum pump only)
- 1 print version of Brief Operating Instructions in the language ordered
- Optional accessories

# Accessories

The following are the most important accessories available at the time this documentation was issued.

► For accessories not listed here, please contact your Service or Sales Center.

Order no.	Bottle tray + bottles + cover				
71162811	Bottle tray + 2 x 3.8 liter (1.00 US gal.) glass + cover				
71111155	Bottle tray + 12 x 2 liter (0.53 US gal.) PE wedge-shaped bottle + cover				
71111156	Bottle tray + 24 x 1 liter (0.26 US gal.) PE wedge-shaped bottle + cover				
71111157	Bottle tray + $12 \times 1$ liter (0.26 US gal.) + $6 \times 2$ liter (0.53 US gal.) PE wedge-shaped bottle + cover				

Order no.	Distributor plate; centering plate			
71111163	Centering plate for bottle tray with wedge-shaped bottles			
71186013	Centering plate for 4 x 5 liters Schott DURAN GLS 80 bottles			

Order no.	Bottles + covers				
71162812	3.8 liter (1.00 US gal.) glass + cover, 1 pc.				
71111169	13 liter (3.43 US gal.) PE + cover, 1 pc.				
71111170	25 liter (5.28 US gal.) PE + cover, 1 pc.				
71111172	30 liter (7.92 US gal.) PE + cover, 1 pc.				
71111173	60 liter (15.8 US gal.) PE + cover, 1 pc.				
71111176	1 liter (0.26 US gal.) PE wedge-shaped bottle + cover, 24 pcs.				
71111178	2 liter (0.53 US gal.) PE wedge-shaped bottle + cover, 12 pcs				

Order no.	Complete suction line				
71111233	Suction line ID 10 mm (3/8"), PVC clear, reinforced fabric, length 10 m (33 ft), suction head V4A				
71111234	Suction line ID 10 mm (3/8"), EPDM black, length 10 m (33 ft), suction head V4A				
71111235	Suction line ID 13 mm (1/2"), PVC green, reinforced spiral wire, length 10 m (33 ft), suction head V4A				
71111236	Suction line ID 13 mm (1/2"), EPDM black, length 10 m (33 ft), suction head V4A				
71111237	Suction line ID 16 mm (5/8"), PVC green, reinforced spiral wire, length 10 m (33 ft), suction head V4A				
71111238	Suction line ID 16 mm (5/8"), EPDM black, length 10 m (33 ft), suction head V4A				
71111239	Suction line ID 19 mm (3/4"), PVC green, reinforced spiral wire, length 10 m (33 ft), suction head V4A				
71111240	Suction line ID 19 mm (3/4"), EPDM black, length 10 m (33 ft), suction head V4A				

Order no.	Terminated hose: vacuum pump			
71111188	Dosing hose to distributor, 2 pcs, material: silicon			
71111189	Dosing hose to distributor, 25 pcs, material: silicon			

Order no.	Terminated hose: peristaltic pump			
71111191	Pump tubing, 2 pcs; material: silicon			
71111192	Pump tubing, 25 pcs; material: silicon			

Order no.	Retrofit kits				
71111195	Kit CSF48: Retrofit kit distribution assembly (distribution arm, distribution drive)				
71111196	Kit CSF48: Retrofit kit casters				
71111197	Kit CSF48: Retrofit kit stand, V2A; 304(x)				
71111198	Kit CSF48: Retrofit kit stand, V4A; 316(x)				
71111199	Kit CSF48: Retrofit kit for flow assembly, without stand; with stand cover V2A; 304(x)				
71111200	Kit CSF48: Retrofit kit for flow assembly, without stand; with stand cover V4A; 316(x)				
71111205	Kit CSF48: Retrofit kit for temperature sensor PT1000				
71111206	Kit CSF48: Retrofit kit 1x digital sensor, Memosens protocol + 2x output 0/4-20mA (hardware + software)				
71111208	Kit CSF48: Retrofit kit 2x digital sensor, Memosens protocol + 2x output 0/4-20mA (hardware + software)				
71111210	Kit CSF48: Retrofit kit 1x to 2x digital sensor, Memosens protocol + 2x output 0/4-20mA (software)				
71146969	Kit CSF48: Retrofit kit 2x digital sensor + 2x output 0/4-20mA and extension backplane				
71136999	Kit CSF48: Retrofit kit service interface (CDI flange connector, counter nut)				
71136885	Kit CSF48: Retrofit kit relay (2x + cable set)				
71136101	Kit CSF48: Retrofit kit door stop (2x)				
71184459	Kit CSF48: Retrofit kit BASE-E module + backplane extension				
71207321	Kit CSF48: Sample distribution 24 x 2 liters				
71111053	Kit CM442/CM444/CM448/CSF48/CA80: extension module AOR; 2 x relay, 2 x $0/4$ to 20 mA analog output				
71125375	Kit CM442/CM444/CM448/CSF48/CA80: extension module 2R; 2 x relay				
71125376	Kit CM442/CM444/CM448/CSF48/CA80: extension module 4R; 4 x relay				
71135632	Kit CM442/CM444/CM448/CSF48/CA80: extension module 2AO; 2 x 0/4 to 20 mA analog output				
71135633	Kit CM442/CM444/CM448/CSF48/CA80: extension module 4A0; 4 x 0/4 to 20 mA analog output				
71135631	Kit CM444/CM448/CSF48: Extension module 2DS; 2 x digital sensor, Memosens				
71135634	Kit CM442/CM444/CM448/CSF48/CA80: extension module 485; Ethernet configuration; can be extended to PROFIBUS DP or Modbus RS485 or Modbus TCP. This requires an additional activation code which can be ordered separately (see Communication; software).				
71135638	Kit CM444R/CM448R/CSF48/CA80: extension module DIO; 2 x digital input; 2 x digital output; auxiliary power supply for digital output				
71135639	Kit CM442/CM444/CM448/CSF48/CA80: extension module 2AI; 2 x 0/4 to 20 mA analog input				
71140888	Upgrade kit CM442/CM444/CM448/CSF48; extension module 485; PROFIBUS DP (+ Ethernet configuration)				
71140889	Upgrade kit CM442/CM444/CM448/CSF48/CA80; extension module 485; Modbus RS485 (+ Ethernet configuration)				
71140890	Upgrade kit CM442/CM444/CM448/CSF48/CA80; extension module 485; Modbus TCP (+ Ethernet configuration)				

Order no.	Retrofit kits				
71219868	Upgrade kit CM442/CM444/CM448/CM442R/CM444R/CM448R/CSF48; extension module 485; EtherNet/IP (+ Ethernet configuration)				
71140891	Kit CM444/CM448: Upgrade code for 2 x 0/4 to 20 mA for BASE-E				
71107456	Kit CM442/CM444/CM448/CSF48: M12 socket for digital sensors; pre-terminated				
71140892	Kit CM442/CM444/CM448/CSF48: M12 socket for PROFIBUS DP/Modbus RS485; B-coded, pre-terminated				
71140893	Kit CM442/CM444/CM448/CSF48: M12 socket for Ethernet; D-coded, preterminated				

Order no.	Communication; software				
71110815	SD card, 1 GB, Industrial Flash Drive				
51516983	Commubox FXA291 + FieldCare Device Setup				
71129799	Field Data Manager software; 1 license, analysis report				
71127100	D card with Liquiline Firmware, 1 GB, Industrial Flash Drive				
71128428	Activation code for digital HART communication				
71367524	Activation code for Heartbeat Verification and Monitoring				
71135635	Activation code for PROFIBUS DP				
71135635	Activation code for PROFIBUS DP				
71135637	Activation code for Modbus TCP				
71219871	Activation code for EtherNet/IP				
71211288	Activation code for feedforward control				
71211289	Activation code for measuring range switch				
71249548	Kit CA80: activation code for 1st digital sensor input				
71249555	Kit CA80: activation code for 2nd digital sensor input				

# Measuring cable

## Memosens data cable CYK10

- For digital sensors with Memosens technology
- Product Configurator on the product page: www.endress.com/cyk10



Technical Information TI00118C

## Measuring cable CYK81

- Unterminated cable for extending sensor cables (e.g. Memosens, CUS31/CUS41)
- 2 x 2 cores, twisted with shielding and PVC sheath (2 x 2 x 0.5 mm² + shielding)
- Sold by meter, Order No.: 51502543

#### Sensors

## Glass electrodes

## **Orbisint CPS11D**

- pH sensor for process technology
- With dirt-repellent PTFE diaphragm
- Product Configurator on the product page: www.endress.com/cps11d



Technical Information TI00028C

# Memosens CPS31D


- pH electrode with gel-filled reference system with ceramic diaphragm
- Product Configurator on the product page: www.endress.com/cps31d



Technical Information TI00030C


#### Ceraliquid CPS41D

- pH electrode with ceramic junction and KCl liquid electrolyte
- Product Configurator on the product page: www.endress.com/cps41d




#### Ceragel CPS71D

- pH electrode with reference system including ion trap
- Product Configurator on the product page: www.endress.com/cps71d




## **Orbipore CPS91D**

- pH electrode with open aperture for media with high dirt load
- Product Configurator on the product page: www.endress.com/cps91d



## Orbipac CPF81D


- Compact pH sensor for installation or immersion operation
- In industrial water and wastewater
- Product Configurator on the product page: www.endress.com/cpf81d



#### Pfaudler electrodes

#### Ceramax CPS341D


- pH electrode with pH-sensitive enamel
- Meets highest demands of measuring accuracy, pressure, temperature, sterility and durability
- Product Configurator on the product page: www.endress.com/cps341d



#### **ORP** sensors


#### **Orbisint CPS12D**

- ORP sensor for process technology
- Product Configurator on the product page: www.endress.com/cps12d




#### Ceraliquid CPS42D

- ORP electrode with ceramic junction and KCl liquid electrolyte
- Product Configurator on the product page: www.endress.com/cps42d



## Ceragel CPS72D

- ORP electrode with reference system including ion trap
- Product Configurator on the product page: www.endress.com/cps72d



#### Orbipac CPF82D

- Compact ORP sensor for installation or immersion operation in process water and wastewater
- Product Configurator on the product page: www.endress.com/cpf82d



#### **Orbipore CPS92D**

- ORP electrode with open aperture for media with high dirt load
- Product Configurator on the product page: www.endress.com/cps92d

Technical Information TI00435C

## pH ISFET sensors

#### Tophit CPS441D

- Sterilizable ISFET sensor for low-conductivity media
- Liquid KCl electrolyte
- Product Configurator on the product page: www.endress.com/cps441d



Technical Information TI00352C

## **Tophit CPS471D**

- Sterilizable and autoclavable ISFET sensor for food and pharmaceutics, process engineering
- Water treatment and biotechnology
- Product Configurator on the product page: www.endress.com/cps471d



Technical Information TI00283C

# **Tophit CPS491D**

- ISFET sensor with open aperture for media with high dirt load
- Product Configurator on the product page: www.endress.com/cps491d



Technical Information TI00377C

#### Conductivity sensors with inductive measurement of conductivity

#### Indumax CLS50D

- High-durability inductive conductivity sensor
- For standard and hazardous area applications
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cls50d



Technical Information TI00182C

#### Conductivity sensors with conductive measurement of conductivity

#### Condumax CLS15D

- Conductive conductivity sensor
- For pure water, ultrapure water and hazardous area applications
- Product Configurator on the product page: www.endress.com/CLS15d



Technical Information TI00109C

#### Condumax CLS16D

- Hygienic, conductive conductivity sensor
- For pure water, ultrapure water and Ex applications
- With EHEDG and 3A approval
- Product Configurator on the product page: www.endress.com/CLS16d



Technical Information TI00227C

## Condumax CLS21D

- Two-electrode sensor in plug-in head version version
- Product Configurator on the product page: www.endress.com/CLS21d



Technical Information TI00085C

## Memosens CLS82D

- Four-electrode sensor
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cls82d



Technical Information TI01188C

## Oxygen sensors

#### Oxymax COS22D

- Sterilizable sensor for dissolved oxygen
- With Memosens technology or as an analog sensor
- Product Configurator on the product page: www.endress.com/cos22d



Technical Information TI00446C

#### Oxymax COS51D

- Amperometric sensor for dissolved oxygen
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cos51d



Technical Information TI00413C

#### Oxymax COS61D

- Optical oxygen sensor for drinking water and industrial water measurement
- Measuring principle: quenching
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cos61d



Technical Information TI00387C

## Memosens COS81D

- Sterilizable, optical sensor for dissolved oxygen
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cos81d



Technical Information TI01201C

#### Chlorine sensors

#### CCS142D

- Membrane-covered amperometric sensor for free chlorine
- Measuring range 0.01 to 20 mg/l
- With Memosens technology
- Product Configurator on the product page: www.endress.com/ccs142d



Technical Information TI00419C

#### Ion-selective sensors

## ISEmax CAS40D

- Ion selective sensors
- Product Configurator on the product page: www.endress.com/cas40d



Technical Information TI00491C

# **Turbidity sensors**

#### **Turbimax CUS51D**

- For nephelometric measurements of turbidity and solids in wastewater
- 4-beam scattered light method
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cus51d



Technical Information TI00461C

#### **Turbimax CUS52D**

- Hygienic Memosens sensor for turbidity measurement in drinking water, process water and in utilities
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cus52d



Technical Information TI01136C

## SAC and nitrate sensors

## Viomax CAS51D

- SAC and nitrate measurement in drinking water and wastewater
- With Memosens technology
- Product Configurator on the product page: www.endress.com/cas51d



Technical Information TI00459C

## Interface measurement

## **Turbimax CUS71D**

- Immersion sensor for interface measurement
- Ultrasonic interface sensor
- Product Configurator on the product page: www.endress.com/cus71d



Technical Information TI00490C





