Safety Instructions Micropilot FMR20

4-20 mA HART, Modbus RS485

II 1 G Ex ia IIC T4 Ga II 1/2 G Ex ia IIC T4 Ga/Gb



XA02548F-A/00/EN/

01.21 71544593 2021-09-14





Micropilot FMR20

4-20 mA HART, Modbus RS485

Table of contents

| Associated documentation | . 4 |
|---|-----|
| Supplementary documentation | . 4 |
| Manufacturer's certificates | . 4 |
| Manufacturer address | 4 |
| Other standards | . 4 |
| Extended order code | . 5 |
| Safety instructions: General | . 8 |
| Safety instructions: Special conditions | 8 |
| Safety instructions: Installation | 9 |
| Safety instructions: Zone 0 | 11 |
| Connection data | 11 |

| Associated documentation | This document is an integral part of the following Operating Instructions: |
|--------------------------------|--|
| | HART BA01578F/00 |
| | Modbus BA01931F/00 |
| Supplementary documentation | Explosion-protection brochure: CP00021Z/11 The Explosion-protection brochure is available: In the download area of the Endress+Hauser website: |
| | www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP00021Z On the CD for devices with CD-based documentation |
| Manufacturer's certificates | UK Declaration of Conformity |
| | Declaration Number: UK_00168 |
| | The UK Declaration of Conformity is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Declaration -> Type: UKCA Declaration -> Product Code: |
| | UKCA type-examination certificate |
| | Certificate number: CML 21UKEX2451X |
| | List of applied standards: See UK Declaration of Conformity. |
| Manufacturer address | Endress+Hauser SE+Co. KG Hauptstraße 1 79689 Maulburg, Germany |
| | Address of the manufacturing plant: See nameplate. |
| Other standards | Among other things, the following standards shall be observed in their current version for proper installation: IEC/EN 60079-14: "Explosive atmospheres - Part 14: Electrical installations design, selection and erection" EN 1127-1: "Explosive atmospheres - Explosion prevention and |
| | protection - Part 1: Basic concepts and methodology" |

Extended The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

| FMR20 | - | ********** | + | A*B*C*D*E*F*G* |
|------------------|---|---------------------------|---|---------------------------|
| (Device type) | | (Basic specifications) | | (Optional specifications) |

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Micropilot

The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type FMR20

Basic specifications

| Position 1, 2 (Approval) | | |
|--------------------------|-------|-------------------------------------|
| Selected op | otion | Description |
| FMR20 | UA | UK Ex II 1 G Ex ia IIC T4T1 Ga |
| | UB | UK Ex II 1/2 G Ex ia IIC T4T1 Ga/Gb |

| Position 3 (Power supply, Output, Operation) | | |
|--|------|---|
| Selected opt | tion | Description |
| FMR20 | А | 2-wire, 4-20 mA HART; HART configuration |
| | Р | 2-wire; 4-20mA HART; HART/Bluetooth (App) configuration |
| | R | 4-wire; Modbus RS485 |

| Position 4, 5 (Antenna, Max. Measuring Range) | | |
|---|------|--|
| Selected op | tion | Description |
| FMR20 | BM | 40mm/1-1/2"; 10m liquid -40°C80°C/-40176°F |
| | BN | 80mm/3"; 20m liquid -40°C80°C/-40176°F |

| Position 6, 7, 8 (Process Connection Rear Side, Material) | | |
|---|------|---|
| Selected op | tion | Description |
| FMR20 | VCE | Thread ASME MNPT1; PVDF; FNPT1/2 conduit connection |
| | WDE | Thread G1 ISO228; PVDF |

| Position 9, 2 | Position 9, 10, 11 (Process Connection Front Side, Material) | | |
|---------------|--|--|--|
| Selected opt | tion | Description | |
| FMR20 | RPF | UNI slip on flange 3"/DN80/80; PP max 4bar abs./58psia, suitable for 3" 150lbs/DN80 PN16/10K 80 | |
| | RRF | UNI slip on flange 4"/DN100/100; PP max 4bar abs./58psia, suitable for 4" 150lbs/DN100 PN16/10K 100 | |
| | RSF | UNI slip on flange 6"/DN150/150; PP max 4bar abs./58psia, suitable for 6" 150lbs/DN150 PN16/10K 150 | |
| | VEE | Thread ASME MNPT1-1/2; PVDF | |
| | VFE | Thread ASME MNPT2; PVDF | |
| | WFE | Thread ISO228 G1-1/2; PVDF | |
| | WGE | Thread ISO228 G2; PVDF | |
| | XR0 | Mounting customer side w/o flange | |

| Position 12 (Cable Length) | | |
|----------------------------|------|-------------|
| Selected op | tion | Description |
| FMR20 | А | ft |
| | 1 | 5m |
| | 2 | 10m |
| | 3 | 20m |
| | 8 | m |


Optional specifications

| ID Rx (Accessory Enclosed) | | |
|----------------------------|----|---|
| Selected option | | Description |
| FMR20 | RA | UNI flange 2"/DN50/50, PP, front side max 4bar abs./58psia, suitable for NPS 2" 150lbs/DN50 PN16/10K 50 |
| | RB | UNI flange 2"/DN50/50, PP, rear side max 4bar abs./58psia, suitable for NPS 2" 150lbs/DN50 PN16/10K 50 |
| | RD | UNI flange 3"/DN80/80, PP, front side max 4bar abs./58psia, suitable for NPS 3" 150lbs/DN80 PN16/10K 80 |
| | RE | UNI flange 3"/DN80/80, PP, rear side max 4bar abs./58psia, suitable for NPS 3" 150lbs/DN80 PN16/10K 80 |
| | RG | UNI flange 4"/DN100/100, PP, front side max 4bar abs./58psia, suitable for NPS 4" 150lbs/DN100 PN16/10K 100 |
| | RH | UNI flange 4"/DN100/100, PP, rear side max 4bar abs./58psia, suitable for NPS 4" 150lbs/DN100 PN16/10K 100 |
| | RK | Swivelling mounting bracket for installation in manhole above sewer |
| | RL | Horizontal mounting bracket for installation in limited space in sewer shaft |
| | R1 | Weather protection cover, PVDF |
| | R2 | Ceiling mounting bracket, 316L |
| | R3 | Mounting bracket adjustable, 316L |
| | R5 | Remote Display RIA 15, ex= explosion proof approval, field enclosure |
| | R6 | HART communication resistor Ex / non Ex |
| | R7 | Flooding protection tube, metallized PBT-PC, suitable for 40mm/1-1/2" antenna with G1-1/2 front side connection |
| | R8 | Flooding protection tube, metallized PBT-PC, suitable for 80mm/3" antenna |

| Safety instructions: General | Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device: Be suitably qualified for their role and the tasks they perform Be trained in explosion protection Be familiar with national regulations Install the device according to the manufacturer's instructions and national regulations. Do not operate the device outside the specified electrical, thermal and mechanical parameters. Only use the device in media to which the wetted materials have sufficient durability. Avoid electrostatic charging: Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates,) Of isolated capacities (e.g. isolated metallic plates) Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser. |
|------------------------------------|--|
| Safety instructions: | Permitted ambient temperature range at the electronics enclosure: For temperature classes T4T1: –40 °C \leq T_a \leq +80 °C |
| Special conditions | Permitted process temperature range: For temperature classes T4T1: -40 °C $\leq T_p \leq +80$ °C |
| | Avoid electrostatic charging of the enclosure (e.g. friction, cleaning, maintenance, strong medium flow). In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic surfaces. In the event of additional or alternative special varnishing on the enclosure or other metal parts: |

- Observe the danger of electrostatic charging and discharge.Do not rub surfaces with a dry cloth.

Safety instructions: Installation



e 1

- A Zone 0, Zone 1
- 1 Tank; Zone 0, Zone 1
- 2 Micropilot FMR20
- 3 Terminal box (optional)
- 4 Controlling unit
- After aligning (rotating) the enclosure, retighten the fixing screw (see Operating Instructions).
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.
- Continuous service temperature of the connecting cable: -40 °C to $\ge +80$ °C.

Intrinsic safety

- The device is only suitable for connection to certified, intrinsically safe equipment with explosion protection Ex ia / Ex ib.
- The intrinsically safe input power circuit of the device is isolated from ground. If the device is only equipped with one input, the dielectric strength of the input is at least 500 V_{rms} . If the device is equipped with more than one input, the dielectric strength of each individual input to ground is at least 500 V_{rms} , and the dielectric strength of the inputs vis-à-vis one another is also at least 500 V_{rms} .
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- When the device is connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC and IIB, the type of protection changes to Ex ib IIC and Ex ib IIB. Do not operate the antenna in Zone 0 if connecting to an intrinsically safe circuit of Category Ex ib.
- When the intrinsically safe Ex ia circuits of the device are connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC or IIB, the type of protection changes to Ex ib [ia] IIC or Ex ib [ia] IIB. Regardless of the power supply, all the internal circuits correspond to Ex ia IIC type of protection (e.g. service interface, external display, sensor).

Connection to Modbus RS485

- Comply with the installation and safety instructions in the Operating Instructions.
- The bus and the devices must be galvanically isolated from each other.

| Safety instructions: Zone 0 | In the event of potentially explosive vapor/air mixtures, only operate the device under atmospheric conditions. Temperature: -40 to +80 °C Pressure: 80 to 110 kPa (0.8 to 1.1 bar) Air with normal oxygen content, usually 21 % (V/V) If no potentially explosive mixtures are present, or if additional protective measures have been taken, the device may also be operated under non-atmospheric conditions in accordance with the manufacturer's specifications. Associated devices with galvanic isolation between the intrinsically safe and non-intrinsically safe circuits are preferred. Only use the device in media to which the SilGel 612 EH potting compound of the electronic insert and the enclosure made of PVDF Kynar 720 have sufficient durability. If there is a risk of dangerous potential differences within Zone 0 (e.g. through the occurrence of atmospheric electricity), implement suitable measures for intrinsically safe circuits in Zone 0. |
|-----------------------------------|---|
| Connection data | When using the internal overvoltage protection: No changes to the connection values. |
| | Exia |
| | Power supply and signal circuit with protection type: intrinsic safety Ex ia IIC, Ex ia IIB. |
| | Basic specification, Position 3 = A, P |
| | Cable blue (-), brown (+) |
| | Power supply: |
| | U _i = 30 V I _i = 100 mA P _i = 750 mW |
| | effective inner inductance $L_i = 35 \ \mu H$ effective inner capacitance $C_i = 15 \ nF$ |

Basic specification, Position 3 = R

| Cable blue (-), brown (+), white (D0), black (D1) | |
|---|---|
| Power supply | RS485 |
| $U_i = 30 V$ $I_i = 100 mA$ $P_i = 650 mW$ | $\begin{array}{l} U_{i} = U_{o} = 4.2 \ V \\ I_{i} = 4.8 \ A \\ I_{o} = 149 \ mA \end{array}$ |
| effective inner inductance L_i = 20 μH effective inner capacitance C_i = 10 nF | effective inner inductance L_i = negligible effective inner capacitance C_i = 97 μF |
| cable inductance L_{cable} = 0.8 $\mu H/m$ cable capacitance C_{cable} = 45 pF/m | cable inductance L_{cable} = 0.8 $\mu H/m$ cable capacitance C_{cable} = 45 pF/m |



71544593

www.addresses.endress.com

