Technical Information iTHERM TT411

Welded thermowell



Use in hygienic and aseptic applications in the food & beverages and pharmaceutical industries

Applications

- Specially designed for use in hygienic and aseptic applications in the Food & Beverages and Life Sciences industries
- Pressure range up to 40 bar (580 psi)
- For increased protection requirements of the temperature sensor regarding physical and chemical effects
- For use in pipes and containers or tanks
- Ideally suited to all measuring points that require regular recalibration by simply replacing the insert in closed processes

Your benefits

- iTHERM QuickNeck cost and time savings thanks to simple, tool-free recalibration of the insert used
- Over 50 hygienic process connections
- Global portfolio with metric and imperial versions
- International certification: 3-A Sanitary Standard, EHEDG, ASME BPE, FDA, TSE Certificate of Suitability
- Optional: 1.4435 material, delta ferrite content < 0.5%
- Fast response time owing to reduced tips with thin walls
- State of the art T-pieces and elbow pieces, no welds and dead legs with best-inclass hygienic design



Installation


Orientation

No restrictions. However, self-draining in the process must be guaranteed. If there is an opening to detect leaks at the process connection, this opening must be at the lowest possible point.

Installation instructions

The immersion length of the thermometer can influence the accuracy. If the immersion length is too small then errors in the measurement are caused by heat conduction via the process connection and the container wall. If installing into a pipe then the immersion length should ideally be half of the pipe diameter.

Installation possibilities: Pipes, tanks or other plant components




A00089

- 1 Installation examples
- 1, 2 Perpendicular to flow direction, installed at a min. angle of 3° to ensure self-draining
- 3 On elbows
- 4 Inclined installation in pipes with a small nominal diameter
- U Immersion length
- In the case of pipes with a small nominal diameter, it is advisable for the tip of the thermometer to project well into the process so that it extends past the pipe axis. Installation at an angle (4) could be another solution. When determining the immersion length or installation depth all the parameters of the thermometer and of the medium to be measured must be taken into account (e.g. flow velocity, process pressure).
- The requirements of the EHEDG and the 3-A Sanitary Standard must be adhered to. Installation instructions EHEDG/cleanability: Lt \leq (Dt-dt) Installation instructions 3-A/cleanability: Lt \leq 2(Dt-dt)

Pay attention to the exact position of the sensor element in the thermometer tip.

2




- StrongSens or TrustSens at 5 to 7 mm (0.2 to 0.28 in) 1
- QuickSens at 0.5 to 1.5 mm (0.02 to 0.06 in)
- Thermocouple (not grounded) at 3 to 5 mm (0.12 to 0.2 in)
- Wire wound sensor at 5 to 20 mm (0.2 to 0.79 in)
- Standard thin-film sensor at 5 to 10 mm (0.2 to 0.39 in)


To keep the influence of heat dissipation to a minimum and to achieve the best possible measurement results, 20 to 25 mm (0.79 to 0.98 in) should be in contact with the medium in addition to the actual sensor element.

This results in the following recommended minimum immersion lengths

- TrustSens or StrongSens 30 mm (1.18 in)
- QuickSens 25 mm (0.98 in)
- Wire wound sensor 45 mm (1.77 in)
- Standard thin-film sensor 35 mm (1.38 in)

It is particularly important to take this into consideration for T-pieces, as the immersion length is very short on account of their design, and the measured error is higher as a result. It is therefore recommended to use elbow pieces with QuickSens sensors.





Operating Instructions BA02023T

Process

Process temperature range	Maximum −200 to +650 °C (−328 to +1202 °F) \rightarrow 🗎 11				
Thermal shock	Thermal shock resistance in CIP/SIP process with a temperature increase and decrease from +5 to +130 $^{\circ}$ C (+41 to +266 $^{\circ}$ F) within 2 seconds.				
Process pressure range	The maximum possible process pressure depends on various influencing factors, such as the design.				


process connection and process temperature. For information on the maximum possible process pressures for the individual process connections, see the Process connection section. $\rightarrow \triangleq 11$

It is possible to check the mechanical loading capacity as a function of the installation and process conditions online in the TW Sizing Module for protection tubes in the Endress+Hauser Applicator software. This is valid for DIN thermowell calculations. See 'Accessories' section.

Example of the permitted flow velocity depending on the immersion length and process medium

The highest flow velocity tolerated by the protection tube diminishes with increasing insert immersion length exposed to the stream of the fluid. In addition, it is dependent on the diameter of the tip of the protection tube, the medium type, process temperature and process pressure. The

following figures exemplify the maximum permitted flow velocities in water and superheated steam at a process pressure of 40 bar (580 PSI).



 \blacksquare 2 Permitted flow velocities, protection tube diameter 9 mm (0.35 in)

- A Medium water at $T = 50 \,^{\circ}\text{C}$ (122 °F)
- *B* Medium superheated steam at $T = 160 \,^{\circ}\text{C}$ (320 °F)
- L Immersion length exposed to flow
- v Flow velocity

Medium - state of aggregation

Gaseous or liquid (also with high viscosity, e.g. yogurt).

Mechanical construction

Design, dimensions


All dimensions in mm (in). The design depends on the thermowell version:

- Diameter 6 mm ($\frac{1}{4}$ in)
- Diameter 9 mm (0.35 in)
- Diameter 12.7 mm (½ in)
- \blacksquare T-piece and elbow piece thermowell version as per DIN 11865/ASME BPE for weld-in
- Various dimensions, such as the immersion length U for example, are variable values and are therefore indicated as items in the following dimensional drawings.

Variable dimensions:

Position	Description
L	Thermowell length (U+T)
В	Thermowell base thickness: predefined, depends on thermowell version (see also the individual table data)
Т	Length of thermowell lagging: variable or predefined, depends on thermowell version (see also the individual table data)
U	Immersion length: variable, depending on the configuration

Thermowell diameter 6 mm (1/4 in)




№ 3 Thermowell with extension neck connection G3/8" and various process connection versions:

- 1
- Clamp version Without process connection 2
- 3 Spherical compression fitting TK40
- Metal sealing system M12x1
- 5 Metal sealing system G½"
- Cylindrical weld-in adapter ϕ 12 x 40 mm 6
- Cylindrical weld-in adapter ϕ 30 x 40 mm
- Spherical-cylindrical weld-in adapter $\phi 30~x~40~mm$
- Spherical weld-in adapter $\phi 25~mm$
- Sanitary connection according to DIN 11851 with threaded bottom part iTHERM QuickNeck, torque 5 Nm (3.69 lbf ft), glued with loctite® 270.

Position	Version	Length
	Metal sealing system M12x1	46 mm (1.81 in)
	Metal sealing system G½"	60 mm (2.36 in)
	Tri-clamp (0.5"-0.75")	24 mm (0.94 in)
	Microclamp (DN8-18)	23 mm (0.91 in)
	Clamp DN12 according to ISO 2852	24 mm (0.94 in)
Longth of themmercial	Clamp DN25/DN40 according to ISO 2852	21 mm (0.83 in)
Length of thermowell lagging T ¹⁾	Sanitary connection DN25/DN32/DN40 according to DIN 11851	29 mm (1.14 in)
	Spherical-cylindrical weld-in adapter	58 mm (2.28 in)
	Cylindrical weld-in adapter $\phi12$ mm (0.47 in)	55 mm (2.17 in)
	Without process connection (only G3/8" thread)	11 mm (0.43 in)
	Cylindrical weld-in adapter	55 mm (2.17 in)
	Spherical weld-in adapter	47 mm (1.85 in)
Immersion length U	Independent of the version	Variable, depending on the configuration
Base thickness B	Reduced tip ϕ 4.3 mm (0.17 in)	2 mm (0.08 in)

1) Depends on the process connection

Thermowell diameter 9 mm (0.35 in)




A0019729

- \blacksquare 4 Thermowell with M24x1.5 connection thread and the following process connection versions:
- 1 Clamp as per ISO2852
- 2 Cylindrical weld-in adapter ϕ 30 x 40 mm
- 3 Spherical-cylindrical weld-in adapter ϕ 30 x 40 mm
- 4 Spherical weld-in adapter Φ25 mm
- 5 Sanitary connection according to DIN 11851
- 6 Aseptic pipe union according to DIN 11864-1 Form A
- 7 Metal sealing system G½"
- 8 Thread according to ISO 228 for Liquiphant weld-in adapter
- 9 APV Inline
- 10 Varivent®
- 11 Ingold connection
- 12 SMS 1147
- 13 Neumo Biocontrol
- 14 Ingold connection, for example with bottom part iTHERM QuickNeck

Position	Version	Length			
Length of thermowell lagging T, without quick-fastening iTHERM QuickNeck		Variable, depending on the configuration			
	SMS 1147, DN25	40 mm (1.57 in)			
With quick-fastening iTHERM QuickNeck, depending on the process connection	SMS 1147, DN38	41 mm (1.61 in)			
	SMS 1147, DN51	42 mm (1.65 in)			
	Varivent [®] , type F, ϕ D = 50 mm (1.97 in)	- 52 mm (2.05 in)			
	Varivent $^{\circ}$, type N, ϕ D = 68 mm (2.67 in)				
	Varivent [®] , type B, ϕ D = 31 mm (1.22 in)	56 mm (2.2 in)			

Position	Version	Length		
	G1" thread according to ISO 228 for Liquiphant weld-in adapter	77 mm (3.03 in)		
	Spherical-cylindrical weld-in adapter	70 mm (2.76 in)		
	Cylindrical weld-in adapter	67 mm (2.64 in)		
	Aseptic pipe union according to DIN11864-A, DN25	42 mm (1.65 in)		
	Aseptic pipe union according to DIN11864-A, DN40	43 mm (1.7 in)		
	Sanitary connection according to DIN 11851, DN32	47 mm (1.85 in)		
	Sanitary connection according to DIN 11851, DN40	47 IIIII (1.63 III)		
	Sanitary connection according to DIN 11851, DN50	48 mm (1.89 in)		
	Clamp according to ISO 2852, DN12			
	Clamp according to ISO 2852, DN25	37 mm (1.46 in)		
	Clamp according to ISO 2852, DN40			
	Clamp according to ISO 2852, DN63.5	39 mm (1.54 in)		
	Clamp according to ISO 2852, DN70			
	Microclamp (DN8-18)	47 mm (1.85 in)		
	Tri-clamp (0.5"-0.75")	46 mm (1.81 in)		
	Ingold connection ϕ 25 mm (0.98 in) x 30 mm (1.18 in)	78 mm (3.07 in)		
	Ingold connection ϕ 25 mm (0.98 in) x 46 mm (1.81 in)	94 mm (3.7 in)		
	Metal sealing system G½"	74 mm (2.91 in)		
	APV-Inline, DN50	51 mm (2.01 in)		
Immersion length U	Independent of the version	Variable, depending on the configuration		
	Reduced tip φ5.3 mm (0.21 in)x 20 mm (0.79 in)	2 mm (0.08 in)		
Base thickness B	Tapered tip ϕ 6.6 mm (0.26 in) x 60 mm (2.36 in)			
	Straight tip			

Thermowell diameter 12.7 mm (1/2 in)



A0019701


- \blacksquare 5 Thermowell with extension neck connection G3/8" and various process connection versions:
- 1 Clamp version
- 2 Cylindrical weld-in adapter ϕ 12.7 mm (0.5 in)
- 3 Spherical weld-in adapter Φ25 mm
- 4 Sanitary connection according to DIN 11851
- 5 Thread according to ISO 228 for Liquiphant weld-in adapter
- 6 Varivent®
- 7 Microclamp, threaded with QuickNeck bottom part, torque 5 Nm (3.69 lbf ft), and glued with loctite $^{\otimes}$ 270, with reduced tip

Welded thermowell at the tip

Position	Version	Length		
Length of thermowell lagging T	Weld-in adapter, cylindrical, ϕ 12.7 mm ($\frac{1}{2}$ in)	12 mm (0.47 in)		
lagging i	All other process connections	65 mm (2.56 in)		
Immersion length U	Independent of the process connection	Variable, depending on the configuration		
	Reduced tip φ5.3 mm (0.21 in)x 20 mm (0.79 in)	2 mm (0.079 in)		
Base thickness B	Reduced tip ϕ 8 mm (0.31 in)x 32 mm (1.26 in)	4 mm (0.16 in)		
	Straight tip	6 mm (0.24 in)		

Thermowell version as T-piece or elbow piece, optimized

No welds, no dead legs



■ 6 Thermowell as per DIN 11865 or ASME BPE

- T-piece with threaded bottom part QuickNeck, torque 5 Nm (3.69 lbf ft), and glued with threadlocking adhesive
- 2 T-piece with extension neck connection G3/8"
- B Elbow piece with extension neck connection G3/8"
- 4 Elbow piece with threaded bottom part QuickNeck, torque 5 Nm (3.69 lbf ft), and glued with threadlocking adhesive
- Pipe sizes as per DIN 11865 series A (DIN), B (ISO) and C (ASME BPE) \rightarrow 🖺 16
- 3-A symbol for nominal diameters >= DN25 for 3-A®, EHEDG and ASME BPE
- EHEDG certification for nominal diameters >= DN25 for 3-A®, EHEDG and ASME BPE
- ASME BPE compliance for nominal diameters >= DN25 for 3-A®, EHEDG and ASME BPE
- IP69K protection class

1

- 1.4435+316L material, delta ferrite content < 0.5%
- Temperature range: -60 to +200 °C (-76 to +392 °F)
- Pressure range: PN25 as per DIN11865
- Due to the short immersion length U in the case of small pipe diameters, the use of iTHERM QuickSens inserts is recommended.

As a general rule, the longer the immersion length U the better the accuracy. For small pipe diameters it is advisable to use elbow pieces to enable a maximum immersion length U.

Suitable immersion lengths for the following thermometers:

- Easytemp TMR35: 83 mm (3.27 in)
- iTHERM TM411: 85 mm (3.35 in)
- iTHERM TM311: 85 mm (3.35 in)
- TrustSens TM371: 85 mm (3.35 in)

Possible combinations of the thermowell versions with the available process connections

		Thermowell diam	iTHERM QuickNeck for Φ9 mm		
Process connection and size	6 mm (½ in)	9 mm (0.35 in)	12.7 mm (½ in)	(0.35 in) 1)	
Without process connection (for installation with compression fitting)	V	-	-	-	
Weld-in adapter			'		
Cylindrical ϕ 12.7 mm ($\frac{1}{2}$ in)	-	-	V	-	
Cylindrical ∮30 x 40 mm	_ ✓	✓	-		
Cylindrical ∮12 x 40 mm		-	-	-	
Spherical-cylindrical ∅30 x 40 mm	✓	4	-		
Spherical ϕ 25 mm (0.98 in)	✓	Ø	V	-	
Clamp according to ISO 2852					
Microclamp/Tri-clamp DN18 (0.75 in)	✓ ²⁾	✓	-	abla	
DN12 - 21.3		•	V	<u>(v</u>)	
DN25 -38 (1 - 1.5 in)	_ ✓	V	V	 ✓	
DN40 - 51 (2 in)		▼.	<u>v</u>	(V)	
DN63.5 (2.5 in)		V	V		
DN70 - 76.5 (3 in)		▼.	Y		
Sanitary connection according to DIN 11851	<u>'</u>	'			
DN25				-	
DN32, DN40		✓	V		
DN50	-			(V)	
Aseptic pipe union according to DIN 11864-1 Form A	'	1	'		
DN25, DN40	-	✓	-		
Metal sealing system	<u>'</u>		'		
M12x1	_ ✓	-		-	
G½"		✓	-	\checkmark	
Thread according to ISO 228 for Liquiphant weld-in adap	ter				
G¾" for FTL20, FTL31, FTL33				-	
G¾" for FTL50	-	✓	\blacksquare	-	
G1" for FTL50				abla	
APV Inline					
DN50	-	✓	-		
Varivent [®]					
Type B, ϕ 31 mm; Type F, ϕ 50 mm ; Type N, ϕ 68 mm	-	4	\checkmark	\checkmark	
Ingold connection					
25 x 30 mm or 25 x 46 mm	-	✓	-		
SMS 1147					
DN25, DN38, DN51	-	✓	-	\checkmark	
Neumo Biocontrol					
D25 PN16, D50 PN16, D65 PN16	-	☑	-	-	

In the case of 6 mm ($\frac{1}{4}$ in) and 12.7 mm ($\frac{1}{2}$ in) diameters, the iTHERM QuickNeck is available for all process connection versions. Microclamp/Tri-clamp DN8 (0.5") only possible in conjunction with a thermowell diameter = 6 mm ($\frac{1}{4}$ in). 1)

Weight

0.5 to 2.5 kg (1 to 5.5 lbs) for standard options.

Material

The temperatures for continuous operation specified in the following table are only intended as reference values for use of the various materials in air and without any significant compressive load. The maximum operating temperatures can be reduced considerably in cases where abnormal conditions such as high mechanical load occur or in aggressive media.

Designation	Short form	Recommended max. temperature for continuous use in air	Properties			
AISI 316L (corresponds to 1.4404 or 1.4435)	X2CrNiMo17-13-2, X2CrNiMo18-14-3	650 °C (1202 °F) 1)	 Austenitic, stainless steel High corrosion resistance in general Particularly high corrosion resistance in chlorine-based and acidic, non-oxidizing atmospheres through the addition of molybdenum (e.g. phosphoric and sulfuric acids, acetic and tartaric acids with a low concentration) Increased resistance to intergranular corrosion and pitting The wetted part in a protective tube is made of 316L or 1.4435+316L passivated with 3% sulfuric acid. 			
1.4435+316L, delta ferrite < 1% or < 0.5%	are met simultaneous	lytical limits, the specifications of both materials (1.4435 and 316L) busly. In addition, the delta ferrite content of the wetted parts is cluding the welding seams (following Basel Standard II); or <0.5%				

 Can be used to a limited extent up to 800 °C (1472 °F) for low compressive loads and in non-corrosive media. Contact your Endress+Hauser sales team for further information.

Surface roughness

Values for wetted surfaces:

Standard surface, mechanically polished ¹⁾	$R_a \leq 0.76 \ \mu m \ (30 \ \mu in)$		
Mechanically polished ¹⁾ , buffed ²⁾	$R_a \le 0.38 \ \mu m \ (15 \ \mu in)$		
Mechanically polished ¹⁾ , buffed and electropolished	$R_a \le 0.38 \ \mu m \ (15 \ \mu in) + electropolished$		

- 1) Or equivalent treatment that guarantees R_a max
- 2) Not compliant with ASME BPE

Process connections

All dimensions in mm (in).


Туре	Version	Dimensions				Tochnical proportion	
Type	version	Φd	ΦD	Φi	Φa	h	Technical properties
Aseptic pipe union according to DIN 11864-1, Form A	DN25	26 mm (1.02 in)	42.9 mm (1.7 in)	26 mm (1.02 in)	29 mm (1.14 in)	9 mm (0.35 in)	 P_{max.} = 40 bar (580 psi) With 3-A[®] symbol and
ØD h	DN40	38 mm (1.5 in)	54.9 mm (2.16 in)	38 mm (1.5 in)	41 mm (1.61 in)	10 mm (0.39 in)	EHEDG certification • ASME BPE compliance

For welding in

Technical properties
 P_{max.} depends on the weld-in process
 With 3-A® symbol and EHEDG certification ASME BPE compliance
ι)

- 1) For thermowell ϕ 12.7 mm ($\frac{1}{2}$ in)
- 2) For thermowell ϕ 6 mm ($\frac{1}{4}$ in)

Releasable process connection




1) Pipes in accordance with DIN 11850

Туре	Version	Dimensions				Technical properties	
Type	Version	φ	ΦD	Φi	Φa	h	reclinical properties
Aseptic pipe union according to DIN 11864-1, Form A	DN25	26 mm (1.02 in)	42.9 mm (1.7 in)	26 mm (1.02 in)	29 mm (1.14 in)	9 mm (0.35 in)	 P_{max.} = 40 bar (580 psi) With 3-A[®] symbol and
ØD	DN40	38 mm (1.5 in)	54.9 mm (2.16 in)	38 mm (1.5 in)	41 mm (1.61 in)	10 mm (0.39 in)	■ ASME BPE compliance

	Version	Di	mensions		_
Туре	φd: ¹⁾	¹⁾		Technical properties	Conformity
Clamp according to ISO 2852	Microclamp ²⁾ DN8-18 (0.5"-0.75") ³⁾ , Form A	25 mm	-		ASME BPE Type A
	Tri-clamp DN8-18 (0.5"-0.75") ³⁾ , Form B	(0.98 in)	-	 P_{max.} = 16 bar (232 psi), depends on clamp ring and suitable seal With 3-A® symbol 	Following ISO 2852 ⁴⁾
D D D D D D D D D D D D D D D D D D D	Clamp DN12-21.3, Form B	34 mm (1.34 in)	16 to 25.3 mm (0.63 to 0.99 in)		ISO 2852
ØD A	Clamp DN25-38 (1"-1.5"), Form B	50.5 mm (1.99 in)	29 to 42.4 mm (1.14 to 1.67 in)	 P_{max.} = 16 bar (232 psi), depends on clamp ring and suitable seal With 3-A® symbol and 	ASME BPE Type B; ISO 2852
0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	Clamp DN40-51 (2"), Form B	64 mm (2.52 in)	44.8 to 55.8 mm (1.76 to 2.2 in)	EHEDG certification (in conjunction with Combifit seal) Can be used with "Novaseptic"	ASME BPE Type B; ISO 2852
Form A	Clamp DN63,5 (2.5"), Form B	77.5 mm (3.05 in)	68.9 to 75.8 mm (2.71 to 2.98 in)	Connect (NA Connect)" which enables flush-mount installation	ASME BPE Type B; ISO 2852
Form B	Clamp DN70-76.5 (3"), Form B	91 mm (3.58 in)	> 75.8 mm (2.98 in)	ilistaliation	ASME BPE Type B; ISO 2852
Form A: In compliance with ASME BPE Type A Form B: In compliance with ASME BPE Type B and ISO 2852					

- 1)
- Pipes in accordance with ISO 2037 and BS 4825 Part 1 Microclamp (not in ISO 2852); no standard pipes DN8 (0.5") only possible with thermowell diameter = 6 mm ($\frac{1}{4}$ in) Groove diameter = 20 mm 2) 3) 4)



Туре	Version	Technical properties
Process adapter	D45	-
Ø50 (1.97) Ø45 (1.77) (0Z)		

		Dimensions			
Туре	Version G	L1 thread length	A	1 (SW/AF)	Technical properties
Thread according to ISO 228 (for Liquiphant weld-in adapter)	G%" for FTL20/31/33 adapter G%" for FTL50 adapter	16 mm (0.63 in)	25.5 mm (1 in)	32	 P_{max.} = 25 bar (362 psi) at max. 150 °C (302 °F) P_{max.} = 40 bar (580 psi) at max. 100 °C (212 °F) With 3-A® symbol and EHEDG certification in conjunction with FTL31/33/50 adapter
A0009572	G1" for FTL50 adapter	18.6 mm (0.73 in)	29.5 mm (1.16 in)	41	■ ASME BPE compliance

Туре	Version			Technical properties			
Type	Version	Φd	ΦA	ΦВ	M	h	reclinical properties
APV Inline							
ØB M Ød ØA A0018435	DN50	69 mm (2.72 in)	99.5 mm (3.92 in)	82 mm (3.23 in)	2xM8	19 mm (0.75 in)	 P_{max.} = 25 bar (362 psi) With 3-A[®] symbol and EHEDG certification ASME BPE compliance

Туре	Version	Dimensions				Technical properties	
Туре	VEISIOII	ΦD	ΦA	ΦВ	h	P _{max} .	
Varivent [®]	Type B	31 mm (1.22 in)	105 mm (4.13 in)	-	22 mm (0.87 in)		
ØA ØB UU ØD	Type F	50 mm (1.97 in)	145 mm (5.71 in)	135 mm (5.31 in)	24 mm (0.95 in)	10 bar (145 psi)	■ With 3-A® symbol and
	Type N	68 mm (2.67 in)	165 mm (6.5 in)	155 mm (6.1 in)	24.5 mm (0.96 in)		EHEDG certification • ASME BPE compliance
A0021307							

The VARINLINE $^{\circ}$ housing connection flange is suitable for weld-in into the conical or torispherical head in tanks or vessels with a small diameter (≤ 1.6 m (5.25 ft)) and up to a wall thickness of 8 mm (0.31 in).

Туре	Technical properties
Varivent® for VARINLINE® housing for installation in pipes	 With 3-A[®] symbol and EHEDG certification ASME BPE compliance
A0009	.64

Vancion	Dimensions						
Version	ΦD	ΦD Φi		P _{max} .			
		DN40: 38 mm (1.5 in)	DN40: 41 mm (1.61 in)				
		DN50: 50 mm (1.97 in)	DN50: 53 mm (2.1 in)	DN40 to DN65: 16 bar (232 psi)			
Type N, according to DIN 11866, series A	68 mm (2.67 in)	DN65: 66 mm (2.6 in)	DN65: 70 mm (2.76 in)				
		DN80: 81 mm (3.2 in)	N80: 81 mm (3.2 in) DN80: 85 mm (3.35 in)				
,		DN100: 100 mm (3.94 in)	DN100: 104 mm (4.1 in)	DN80 to DN150:			
		DN125: 125 mm (4.92 in)	DN125: 129 mm (5.08 in)	10 bar (145 psi)			
		DN150: 150 mm (5.9 in)	DN150: 154 mm (6.06 in)				
		38.4 mm (1.51 in)	42.4 mm (1.67 in)	42.4 mm (1.67 in) to			
Type N, according to EN ISO 1127, series B	68 mm (2.67 in)	44.3 mm (1.75 in)	48.3 mm (1.9 in)	60.3 mm (2.37 in): 16 bar (232 psi)			

Туре				Technical properties
		56.3 mm (2.22 in)	60.3 mm (2.37 in)	
		72.1 mm (2.84 in)	76.1 mm (3 in)	76.1 mm (3 in) to
		82.9 mm (3.26 in)	42.4 mm (3.5 in)	114.3 mm (4.5 in):
		108.3 mm (4.26 in)	114.3 mm (4.5 in)	10 bar (145 psi)
		OD 11/#-24 0 (1.27 :)	OD 11/# 20 1 (1 F :)	
	68 mm (2.67 in)	OD 1½": 34.9 mm (1.37 in)	OD 1½": 38.1 mm (1.5 in)	
Type N, according to DIN 11866, series C		OD 2": 47.2 mm (1.86 in)	OD 2": 50.8 mm (2 in)	OD 1½" to OD 2½": 16 bar (232 psi)
,		OD 2½": 60.2 mm (2.37 in)	OD 2½": 63.5 mm (2.5 in)	
Type N, according to DIN 11866, series C	60 mm (2.67 in)	OD 3": 73 mm (2.87 in)	OD 3": 76.2 mm (3 in)	OD 3" to OD 4": 10 bar (145 psi)
	68 mm (2.67 in)	OD 4": 97.6 mm (3.84 in)	OD 4": 101.6 mm (4 in)	7 CU OU 4 . 10 bai (145 psi)

Due to the short immersion length U, the use of iTHERM QuickSens inserts is recommended.

T-piece, optimized (no welding, no dead legs)

Tymo	Version		Dime	ensions in mm (i	n)	T-desirel
Туре		version	ΦD	L	s 1)	Technical properties
T-piece for weld-in as per DIN 11865 (series A, B and C)	Series A	DN10 PN25	13 mm (0.51 in)			
G3/8"		DN15 PN25	19 mm (0.75 in)			
		DN20 PN25	23 mm (0.91 in)		1.5 mm (0.06 in)	
97. (9.71) E8 97. (0.71) E8		DN25 PN25	29 mm (1.14 in)			
<u>05.1</u>		DN32 PN25	32 mm (1.26 in)			 P_{max.} = 25 bar (362 psi) With 3-A® symbol and EHEDG certification for ≥ DN25 ASME BPE compliance for ≥ DN25
(0.12)	Series B	DN13.5 PN25	13.5 mm (0.53 in)	48 mm (1.89 in)	1.6 mm (0.063 in)	
Ø4.5 (0.18) Ø4.5 (0.18)		DN17.2 PN25	17.2 mm (0.68 in)			
L CO		DN21.3 PN25	21.3 mm (0.84 in)			
		DN26.9 PN25	26.9 mm (1.06 in)			
		DN33.7 PN25	33.7 mm (1.33 in)		2 mm (0.08 in)	
	Series C	DN12.7 PN25 (½")	12.7 mm (0.5 in)		1.65 mm (0.065 in)	
		DN19.05 PN25 (¾")	19.05 mm (0.75 in)			
		DN25.4 PN25 (1")	25.4 mm (1 in)			
		DN38.1 PN25 (1½")	38.1 mm (1.5 in)			

1) Wall thickness

Elbow piece, optimized (no welding, no dead legs)

Т	17			Dimen	nsions		Tarkerian lauranatian
Туре	V	ersion	ΦD	ΦD L1 L2		s 1)	Technical properties
Elbow piece for weld-in as per DIN 11865 (series A, B and C)	Series A	DN10 PN25	13 mm (0.51 in)	24 r (0.95		1.5 mm (0.06 in)	
L2 G3/8"		DN15 PN25	19 mm (0.75 in)	25 r (0.98			
		DN20 PN25	23 mm (0.91 in)	27 r (1.06			
		DN25 PN25	29 mm (1.14 in)	30 r (1.18			
Ø3.1 (0.12) (92.8) 88 (3.26)		DN32 PN25	35 mm (1.38 in)	33 r (1.3			
0.7 (0.03)	Series B	DN13.5 PN25	13.5 mm (0.53 in)	32 r (1.26		1.6 mm (0.063 in)	D 051 (060 i)
<u>Ø4.5</u> (0.18) pp		DN17.2 PN25	17.2 mm (0.68 in)	34 r (1.34			 P_{max.} = 25 bar (362 psi) With 3-A[®] symbol and EHEDG certification for
(0.18) OD		DN21.3 PN25	21.3 mm (0.84 in)	36 r (1.42			≥ DN25 • ASME BPE compliance for ≥ DN25
		DN26.9 PN25	26.9 mm (1.06 in)	29 r (1.14			E BNES
		DN33.7 PN25	33.7 mm (1.33 in)	32 r (1.26		2.0 mm (0.08 in)	
	Series C	DN12.7 PN25 (½")	12.7 mm (0.5 in)	24 r (0.95		1.65 mm (0.065 in)	
		DN19.05 PN25 (¾")	19.05 mm (0.75 in)	25 r (0.98			
		DN25.4 PN25 (1")	25.4 mm (1 in)	28 r (1.1			
		DN38.1 PN25 (1½")	38.1 mm (1.5 in)	35 r (1.38			

1) Wall thickness

Туре	Version, dimensions ∅D x h	Technical properties
Ingold connection		
	ϕ 25 mm (0.98 in) x30 mm (1.18 in) x = 1.5 mm (0.06 in)	P _{max.} = 25 bar (362 psi) A seal is included in the scope of delivery. Material V75SR:
h G1¼" (91.0)	ϕ 25 mm (0.98 in) x46 mm (1.81 in) x = 6 mm (0.24 in)	compliance with FDA, 3-A® Sanitary Standard 18-03 Class 1 and USP Class VI
A0009573		

Tymo	Version		Technical properties		
Туре	VEISIOII	ΦD	ΦA	h	recinical properties
SMS 1147 ØA	DN25	32 mm (1.26 in)	35.5 mm (1.4 in)	7 mm (0.28 in)	
ØD →	DN38	48 mm (1.89 in)	55 mm (2.17 in)	8 mm (0.31 in)	
A0009568	DN51	60 mm (2.36 in)	65 mm (2.56 in)	9 mm (0.35 in)	P _{max.} = 6 bar (87 psi)
Thread adapter nut Sealing ring Counterpart connection					

Туре	Version	Dimensions				Technical properties	
Туре	version	ΦA	ΦВ	ΦD	Ød	h	recinical properties
Neumo Biocontrol ØB	D25 PN16	64 mm (2.52 in)	50 mm (1.97 in)	30.4 mm (1.2 in)	7 mm (0.28 in)	20 mm (0.79 in)	
M	D50 PN16	90 mm (3.54 in)	70 mm (2.76 in)	49.9 mm (1.97 in)	9 mm (0.35 in)	27 mm	 P_{max.} = 16 bar (232 psi) With 3-A® symbol
ØD ØA A0018497	D65 PN25	120 mm (4.72 in)	95 mm (3.74 in)	67.9 mm (2.67 in)	11 mm (0.43 in)	(1.06 in)	

The 316L compression fittings can only be used once due to deformation. This applies to all the components of the compression fittings! A replacement compression fitting must be fastened at another point (grooves in thermowell). PEEK compression fittings must never be used at a temperature that is lower than the temperature present when the compression fitting is secured. This is because the fitting would no longer be leak-tight as a result of heat contraction of the PEEK material.


If stricter requirements must be met, the use of SWAGELOCK or similar fasteners is urgently recommended.

Tip shape

The thermal response time, the reduction of the flow cross-section and the mechanical load that occurs in the process are the criteria that matter when selecting the shape of the tip. Advantages of using reduced or tapered thermometer tips:

- \blacksquare A smaller tip shape has less impact on the flow characteristics of the pipe carrying the medium.
- The flow characteristics are optimized, thereby increasing the stability of the thermowell.
- Endress+Hauser offers users a range of thermowell tips to meet every requirement:
 - Reduced tip with Ø4.3 mm (0.17 in) and Ø5.3 mm (0.21 in): walls of lower thickness significantly reduce the response times of the overall measuring point.
 - Tapered tip with Ø6.6 mm (0.26 in) and reduced tip with Ø8 mm (0.31 in): walls of greater thickness are particularly well suited to applications with a higher degree of mechanical load or wear (e.g. pitting, abrasion etc.).

18



■ 7 Thermowell tips available (reduced, straight or tapered)

Item No.	Thermowell (ØD1)		Insert (ØID)
1	Ø6 mm (½ in)	Reduced tip	Ø3 mm (⅓ in)
2	Ø9 mm (0.35 in)	 Reduced tip with Ø5.3 mm (0.21 in) Straight tip Tapered tip with Ø6.6 mm (0.26 in) 	 Ø3 mm (½ in) Ø6 mm (¼ in) Ø3 mm (½ in)
3	Ø12.7 mm (½ in)	 Reduced tip with Ø5.3 mm (0.21 in) Straight tip Reduced tip with Ø8 mm (0.31 in) 	■ Ø3 mm (½ in) ■ Ø6 mm (¼ in) ■ Ø6 mm (¼ in)

It is possible to check the mechanical loading capacity as a function of the installation and process conditions online in the TW Sizing Module for thermowells in the Endress+Hauser Applicator software. See "Accessories" section.

Certificates and approvals

CE mark

The product meets the requirements of the harmonized European standards. As such, it complies with the legal specifications of the EU directives. The manufacturer confirms successful testing of the product by affixing to it the CE mark.

Hygiene standard

- EHEDG certification, type EL CLASS I. EHEDG-certified/tested process connections in accordance with EHEDG \rightarrow $\stackrel{ riangle}{=}$ 11
- 3-A® authorization no. 1144, 3-A® Sanitary Standard 74-07. Listed process connections → 🖺 11
- ASME BPE, declaration of conformity, can be ordered for options indicated
- FDA-compliant
- All surfaces in contact with the medium are free from materials derived from bovine animals or other livestock (ADI/ISE)

Other standards and quidelines

DIN 43772: Thermowells

CRN approval

The CRN approval is only available for certain thermowell versions. These versions are identified and displayed accordingly during the configuration of the device.

Detailed ordering information is available for your nearest sales organization www.addresses.endress.com or in the Download Area under www.endress.com :

- 1. Select the country
- 2. Select Downloads
- 3. In the search area: select Approvals/approval type
- 4. Enter the product code or device
- 5. Start the search

Areas in contact with medium

The areas of the thermometer in contact with food/product (FCM) comply with the following European regulations:

- (EC) No. 1935/2004, Article 3, paragraph 1, Articles 5 and 17 on materials and articles intended to come into contact with food.
- (EC) No. 2023/2006 on good manufacturing practice for materials and articles intended to come into contact with food.
- (EC) No. 10/2011 on plastic materials and articles intended to come into contact with food.
- FDA-compliant
- All surfaces in contact with medium are produced without animal fats (ADI/TSE)

Surface roughness

- Free from oil and grease for O₂ applications, optional
- PWIS-free (PWIS = paint-wetting impairment substances as per DIL0301), optional

Material certification

The material certificate 3.1 (according to standard EN 10204) can be requested separately. The "short form" certificate includes a simplified declaration with no enclosures of documents related to the materials used in the construction of the single sensor and guarantees the traceability of the materials through the identification number of the thermometer. The data related to the origin of the materials can subsequently be requested by the client if necessary.

Thermowell testing and load capacity calculation

- Thermowell pressure tests are carried out in accordance with the specifications in DIN 43772. With regard to thermowells with tapered or reduced tips that do not comply with this standard, these are tested using the pressure of the corresponding straight thermowells. Tests according to other specifications can be carried out on request. The liquid penetration test verifies that there are no cracks in the welded seams of the thermowell.
- EN1779 helium leak test, PMI test, concentricity test for drilled thermowells, dye penetration test, TW welding, internal hydrostatic pressure, etc. each with inspection certificate
- Load capacity calculation for the thermowell as per DIN43772

Ordering information

Detailed ordering information is available for your nearest sales organization www.addresses.endress.com or in the Product Configurator under www.endress.com :

- 1. Click Corporate
- 2. Select the country
- 3. Click Products
- 4. Select the product using the filters and search field
- 5. Open the product page

The Configuration button to the right of the product image opens the Product Configurator.


Product Configurator - the tool for individual product configuration


- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- \blacksquare Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Accessories


Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories







1) A seal is included in the delivery.




1) A seal is included in the delivery.




1) A seal is included in the delivery.




1) A seal is included in the delivery.



A seal is included in the delivery.



1) A seal is included in the delivery.





Maximum process pressure for the weld-in adapters:

- 25 bar (362 PSI) at maximum 150 °C (302 °F)
- 40 bar (580 PSI) at maximum 100 °C (212 °F)



For more information on the weld-in adapters FTL20/31/33, FTL50, see the Technical Information (TI00426F/00).

Service-specific accessories

Accessories	Description
Applicator	Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum measuring device: e.g. pressure loss, accuracy or process connections. Graphic illustration of the calculation results
	Administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.
	Applicator is available: Via the Internet: https://portal.endress.com/webapp/applicator On CD-ROM for local PC installation.

Configurator	Product Configurator - the tool for individual product configuration • Up-to-the-minute configuration data • Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language • Automatic verification of exclusion criteria • Automatic creation of the order code and its breakdown in PDF or Excel output format • Ability to order directly in the Endress+Hauser Online Shop
	The Configurator is available on the Endress+Hauser website: www.endress.com Click "Corporate" -> Select country -> Click "Products" -> Select the product using the filters and search field -> Open product page -> The "Configure" button to the right of the product image opens the Product Configurator.

W@M	Life cycle management for your plant W@M supports with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records.
	W@M is available: ■ Via the Internet: www.endress.com/lifecyclemanagement ■ On CD-ROM for local PC installation.

Documentation

 $\begin{tabular}{ll} Modular resistance thermometer for hygienic and aseptic applications iTHERM TM411: \\ TI01038T/09/EN \end{tabular}$

Insert iTHERM TS111: TI01014T/09/EN





