71483581 2020-07-01

# Technical Information Proline Prosonic Flow E 100

# Ultrasonic time-of-flight flowmeter



# Cost-efficient ultrasonic time-of-flight flowmeter with integrated temperature measurement

#### Application

- The measuring principle is independent of pressure, density, temperature and conductivity
- Bidirectional measuring of demineralized water for Utilities, e.g. in boiler condensate return lines

#### Device properties

- Accuracy: up to ±0.5 % (flow) or according to EN 1434 Cl. 2, ±2.0 °C (±3.6 °F) (temperature)
- Process temperatures up to 150 °C (302 °F)
- Entire flowmeter made of stainless steel
- 4-20 mA HART, pulse/frequency output
- Local display for reading and monitoring available
- Robust transmitter housing

#### Your benefits

- Long-term stability reliable, robust sensor
- Reducing further measuring point multivariable device
- Dependable flow measurement high turndown (200:1)
- Time-saving local operation without additional software and hardware integrated web server
- Extended calibration intervals integrated device verification due to Heartbeat Technology
- Easy commissioning brief parameter explanations



# Table of contents

About this document	<b>3</b> . 3
Function and system design         Measuring principle         Measuring system         Safety	4
Input	. 5
Output Output signal Signal on alarm Low flow cut off Protocol-specific data	. 8 9
Power supply	<pre>11 11 12 12 12 12 12 12 14 14 14 14</pre>
Performance characteristics	<b>14</b> 14 14 16 16
Installation	<b>16</b> 16 16 17
Environment	<ol> <li>18</li> <li>18</li> <li>18</li> <li>18</li> <li>18</li> <li>18</li> </ol>
Process	<b>18</b> 18 18 18 21 21

System pressure	21 22
Mechanical construction	22 25 27 28 29
Human interface	<b>30</b> 30 30 30 31
Certificates and approvals CE mark RCM-tick symbol HART certification Pressure Equipment Directive Other standards and guidelines	<b>31</b> 31 31 31 31 32
Ordering information	32
Application packages      Heartbeat Technology	<b>32</b> 33
Accessories	<b>33</b> 33 34 34
Supplementary documentation Standard documentation Supplementary device-dependent documentation	<b>35</b> 35 35
Registered trademarks	36

# About this document

#### Symbols

#### Electrical symbols

Symbol	Meaning
	Direct current
$\sim$	Alternating current
$\sim$	Direct current and alternating current
<u>+</u>	<b>Ground connection</b> A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Protective Earth (PE) A terminal which must be connected to ground prior to establishing any other connections.
	<ul><li>The ground terminals are situated inside and outside the device:</li><li>Inner ground terminal: Connects the protectiv earth to the mains supply.</li><li>Outer ground terminal: Connects the device to the plant grounding system.</li></ul>

#### Symbols for certain types of information

Symbol	Meaning
	<b>Permitted</b> Procedures, processes or actions that are permitted.
	<b>Preferred</b> Procedures, processes or actions that are preferred.
×	<b>Forbidden</b> Procedures, processes or actions that are forbidden.
i	<b>Tip</b> Indicates additional information.
	Reference to documentation.
	Reference to page.
	Reference to graphic.
	Visual inspection.

#### Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections
EX	Hazardous area
X	Safe area (non-hazardous area)
≈➡	Flow direction

### Function and system design


Measuring principle

The measuring device measures the flow velocity in the measuring tube based on an offset arrangement of ultrasonic sensors downstream. The design does not cause any pressure loss and does not have any moving parts.

The flow signal is established by alternating an acoustic signal between the sensor pairs and measuring the transit time of each transmission. Then utilizing the fact that sound travels faster with the flow versus against the flow, this differential time (D T) can be used to determine the fluid's velocity between the sensors.

The volume flow rate is established by combining all the flow velocities determined by the sensor pairs with the cross sectional area of the meter body and extensive knowledge about fluid flow dynamics. The design of the sensors and their position ensures that only a short straight run of pipe upstream of the meter is required after typical flow obstructions such as bends in one or two planes.

Advanced digital signal processing and innovative sensor design facilitate constant flow measurement evaluation and reduce sensitivity to multiphase flow conditions and increase measurement reliability.




#### Measuring system


The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.

#### Transmitter



#### Sensor



Safety

#### IT security

Our warranty is valid only if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the settings.

IT security measures, which provide additional protection for the device and associated data transfer, must be implemented by the operators themselves in line with their security standards.

### Input

Measured variable

#### Direct measured variables

- Flow velocity
- Medium temperature
- Sound velocity

#### **Calculated measured variables**

- Volume flow
- Mass flow

#### Measuring range

#### Typically v = 0 to 5 m/s (0 to 16.4 ft/s) with the specified accuracy

#### Flow characteristic values in SI units

Nom diam	ninal neter	Recommended flow	Factory settings		
		min./max. full scale value	Full scale value current output	Pulse value	Low flow cut off (v ~ 0.1 m/s)
[mm]	[in]	[dm³/min]	[dm³/min]	[dm³/pulse]	[dm³/min]
50	2	0 to 720	720	3	14.4
65	2 1/2	0 to 1200	1200	4	24.0
80	3	0 to 1680	1680	6	33.6

Nom diam		Recommended flow	Factory settings		
		min./max. full scale value	Full scale value current output	Pulse value	Low flow cut off (v ~ 0.1 m/s)
[mm]	[in]	[dm³/min]	[dm³/min]	[dm³/pulse]	[dm³/min]
100	4	0 to 2 880	2880	10	57.6
150	6	0 to 6 360	6360	25	127.2

Flow characteristic values in US units

	ninal neter	Recommended flow	Factory settings		
		min./max. full scale value	Full scale value current output	Pulse value	Low flow cut off (v ~ 0.1 m/s)
[in]	[mm]	[gal/min]	[gal/min]	[gal/pulse]	[gal/min]
2	50	0 to 190	190	0.8	3.8
2 1/2	65	0 to 317	317	1.1	6.3
3	80	0 to 444	444	1.6	8.9
4	100	0 to 761	761	2.6	15.2
6	150	0 to 1680	1680	6.6	33.6

#### Flow characteristic values as per EN 1434 Class 2

Flow characteristic values in SI units

	Nominal diameter		ommended f	low	Factory settings	
		$q_i^{(1)}$	q <sub>p</sub> <sup>2)</sup>	q <sub>s</sub> <sup>3)</sup>	Pulse value	Low flow cut off (v ~ 0.1 m/s)
[mm]	[in]	[m³/h]	[m³/h]	[m³/h]	[dm³/pulse]	[dm³/min]
50	2	0.15	15	30	3	0
65	2 1⁄2	0.25	25	50	4	0
80	3	0.40	40	80	6	0
100	4	0.60	60	120	10	0
150	6	1.50	150	300	25	0

1)  $q_i$ : Minimum flow rate = Lowest flow rate at which the flowmeter operates within the limits of error in legal metrology

2) q<sub>p</sub>: Permanent flow rate = Highest flow rate at which the flowmeter operates within the limits of error in legal metrology

3)  $q_s$ : Maximum flow rate = Highest flow rate

#### Flow characteristic values in US units


	ninal neter	Recommended flow		Factory settings		
		$q_{i}$	$\mathbf{q}_{\mathrm{p}}$	qs	Pulse value	Low flow cut off (v ~ 0.1 m/s)
[in]	[mm]	[gal/min]	[gal/min]	[gal/min]	[gal/pulse]	[gal/min]
2	50	0.66	66	132	0.8	0
2 1/2	65	1.10	110	220	1.1	0
3	80	1.76	176	352	1.6	0

	ninal neter	Recommended flow		Factory settings		
		q <sub>i</sub>	$q_p$	q <sub>s</sub>	Pulse value	Low flow cut off (v ~ 0.1 m/s)
[in]	[mm]	[gal/min]	[gal/min]	[gal/min]	[gal/pulse]	[gal/min]
4	100	2.64	264	528	2.6	0
6	150	6.60	660	1320	6.6	0



To calculate the measuring range, use the Applicator sizing tool  $\rightarrow$   $\cong$  34

#### Recommended measuring range



Operable flow range

Over 200:1

# Output

Output signal

#### HART current output

Current output	4-20 mA HART (active)
Maximum output values	<ul> <li>DC 24 V (no flow)</li> <li>22.5 mA</li> </ul>
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0.07 to 999 s
Assignable measured variables	<ul> <li>Volume flow</li> <li>Mass flow</li> <li>Sound velocity</li> <li>Flow velocity</li> <li>Temperature</li> <li>Acceptance rate<sup>1)</sup></li> <li>Signal strength<sup>1)</sup></li> <li>Signal to noise ratio<sup>1)</sup></li> <li>Turbulence<sup>1)</sup></li> <li>Signal asymmetry<sup>2)</sup></li> <li>In range of options increases if the measuring device has one or more application packages.</li> </ul>

1) 2) Only with Heartbeat (Monitoring)

Only with Heartbeat (Monitoring) and dual path version

#### Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output		
Version	Passive, open collector		
Maximum input values	<ul> <li>DC 30 V</li> <li>25 mA</li> </ul>		
Voltage drop	For 25 mA: $\leq$ DC 2 V		
Pulse output			
Pulse width	Configurable: 0.05 to 2 000 ms		

Maximum pulse rate	10000 Impulse/s			
Pulse value	Adjustable			
	Volume flow			
Assignable measured variables	<ul><li>Volume flow</li><li>Mass flow</li></ul>			
Frequency output				
Output frequency	Configurable: 0 to 10 000 Hz			
Damping	Configurable: 0 to 999 s			
Pulse/pause ratio	1:1			
Assignable measured variables	<ul> <li>Volume flow</li> <li>Mass flow</li> <li>Sound velocity</li> <li>Flow velocity</li> <li>Temperature</li> <li>Acceptance rate <sup>1)</sup></li> <li>Signal strength <sup>1)</sup></li> <li>Signal to noise ratio <sup>1)</sup></li> <li>Turbulence <sup>1)</sup></li> <li>Signal asymmetry <sup>2)</sup></li> </ul>			
Switch output				
Switching behavior	Binary, conductive or non-conductive			
Switching delay	Configurable: 0 to 100 s			
Number of switching cycles	Unlimited			
Assignable functions	<ul> <li>Off</li> <li>On</li> <li>Diagnostic behavior</li> <li>Limit value: <ul> <li>Off</li> <li>Volume flow</li> <li>Mass flow</li> <li>Sound velocity<sup>1)</sup></li> <li>Flow velocity</li> <li>Totalizer 1-3</li> <li>Temperature</li> <li>Signal strength<sup>1)</sup></li> <li>Signal to noise ratio<sup>1)</sup></li> <li>Turbulence<sup>1)</sup></li> <li>Signal asymmetry<sup>2)</sup></li> <li>Acceptance rate<sup>1)</sup></li> <li>Flow direction monitoring</li> <li>Status Low flow cut off</li> </ul> </li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>			

1) 2)

Only with Heartbeat (Monitoring) Only with Heartbeat (Monitoring) and dual path version

#### Signal on alarm

Depending on the interface, failure information is displayed as follows:

#### Current output 4 to 20 mA

#### 4 to 20 mA

Failure mode	<ul> <li>Choose from:</li> <li>4 to 20 mA in accordance with NAMUR recommendation NE 43</li> <li>4 to 20 mA in accordance with US</li> <li>Min. value: 3.59 mA</li> <li>Max. value: 22.5 mA</li> <li>Freely definable value between: 3.59 to 22.5 mA</li> <li>Actual value</li> <li>Last valid value</li> </ul>
--------------	---

#### Pulse/frequency/switch output

Pulse output		
Failure mode	Choose from: • Actual value • No pulses	
Frequency output		
Failure mode	Choose from: • Actual value • 0 Hz • Defined value: 0 to 12 500 Hz	
Switch output		
Failure mode	Choose from: • Current status • Open • Closed	

#### Local display

Plain text display	With information on cause and remedial measures
Backlight	Red backlighting indicates a device error.

Status signal as per NAMUR recommendation NE 107

#### Interface/protocol

- Via digital communication: HART protocol
- Via service interface CDI-RJ45 service interface

Plain text display	With information on cause and remedial measures
--------------------	---

Additional information on remote operation  $\rightarrow \cong 30$ 

#### Web browser

Plain text display	With information on cause and remedial measures
--------------------	---

Low flow cut off The switch points for low flow cut off are user-selectable. Protocol-specific data HART Manufacturer ID 0x11 Device type ID 115C 7.5 HART protocol revision Device description files Information and files under: (DTM, DD) www.endress.com HART load Min. 250 Ω

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.			
	Measured variables for PV (primary dynamic variable)  Volume flow Mass flow Sound velocity Flow velocity Temperature Acceptance rate <sup>1)</sup> Signal strength <sup>1)</sup> Signal to noise ratio <sup>1)</sup> Turbulence <sup>1)</sup> Signal asymmetry <sup>2)</sup>			
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable) Volume flow Mass flow Sound velocity Flow velocity Temperature Acceptance rate <sup>1)</sup> Signal strength <sup>1)</sup> Signal to noise ratio <sup>1)</sup> Turbulence <sup>1)</sup> Signal asymmetry <sup>2)</sup> Totalizer 1 Totalizer 2 Totalizer 3			
	The range of options increases if the measuring device has one or application packages.			
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned. A maximum of 8 device variables can be transmitted: <ul> <li>0 = volume flow</li> <li>1 = mass flow</li> <li>2 = sound velocity</li> <li>3 = flow velocity</li> <li>4 = temperature</li> <li>5 = totalizer 1</li> <li>6 = totalizer 2</li> <li>7 = totalizer 3</li> <li>8 = acceptance rate</li> <li>9 = turbulence</li> <li>10 = signal to noise ratio</li> <li>11 = signal asymmetry</li> <li>12 = signal strength</li> </ul>			


1) 2)

Only with Heartbeat (Monitoring) Only with Heartbeat (Monitoring) and dual path version

# Power supply

Terminal assignment

#### Overview: housing version and connection versions



- A Housing version: compact, aluminum coated
- B Housing version: compact, stainless
- 1 Connection version: 4-20 mA HART, pulse/frequency/switch output
- 1.1 Signal transmission: pulse/frequency/switch output
- 1.2 Signal transmission: 4-20 mA HART
- 1.3 Supply voltage

#### Transmitter

Connection version 4-20 mA HART with pulse/frequency/switch output


Order code for "Output", option B

Connection methods av		thods available	Descible options for order order	
"Housing"	Outputs	Power supply	Possible options for order code "Electrical connection"	
Options A, D	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option D: thread NPT <sup>1</sup>/<sub>2</sub>"</li> </ul>	
Order code for "Hou	sina":	• Option <b>D</b> : thread NPT <sup>1</sup> / <sub>2</sub> "		

Order code for "Housing":

Option A: compact, coated aluminum

• Option **D**: compact, stainless



I Terminal assignment 4-20 mA HART with pulse/frequency/switch output


1 Power supply: DC 24 V

- 2 Output 1: 4-20 mA HART (active)
- 3 Output 2: pulse/frequency/switch output (passive)

		Terminal number					
	Order code "Output"	Power supply Output 1		Output 2			
	output	2 (L-) 1 (L+)	27 (-)	26 (+)	25 (-)	24 (+)	
	Option <b>B</b>	DC 24 V	4-20 mA HART	(active)	Pulse/frequ output (		
	Order code for "Output": Option <b>B</b> : 4-20 mA HART v	with pulse/frequency/swite	h output				
Supply voltage	The power unit must be t	tested to ensure it meet	s safety requireme	nts (e.g. l	PELV, SELV).		
	Transmitter						
	For device version with H	IART communication ty	pe: DC 19.2 to 28.8	3 V			
Power consumption	Transmitter						
	Order code for "Output"			I	Maximun Power consum		
	Option <b>B</b> : 4-20 mA HART v	Option <b>B</b> : 4-20 mA HART with pulse/frequency/switch output					
Current consumption	Transmitter						
	Order code for "Output"			Maximum Current consumption		Maximum switch-on current	
	Option <b>B</b> : 4-20mA HART, p	200 mA		30 A (< 0.275 ms)			
Power supply failure	<ul> <li>Totalizers stop at the last value measured.</li> <li>Depending on the device version, the configuration is retained in the device memoryor in the pluggable data memory (HistoROM DAT).</li> <li>Error messages (incl. total operated hours) are stored.</li> </ul>						
Electrical connection	Connecting the transmitter						
	AHousing version: compBHousing version: comp1Cable entry for signal t2Cable entry for supply v	act, stainless ransmission				A004	


#### **Connection examples**

Current output 4 to 20 mA HART




2 Connection example for 4 to 20 mA HART current output (active)

- 1 Automation system with current input (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC
- requirements; observe cable specifications  $\rightarrow \square 14$
- 3 Connection for HART operating devices  $\rightarrow \cong 30$
- 4 Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load
- 5 Analog display unit: observe maximum load
- 6 Transmitter



- 3 Connection example for 4 to 20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications  $\rightarrow \cong 14$
- 4 Analog display unit: observe maximum load
- 5 Transmitter

#### Pulse/frequency output



- Connection example for pulse/frequency output (passive)
- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values  $\rightarrow \square 7$

#### Switch output

	6 5 Connection example for switch output (passive)			
	<ol> <li>Automation system with switch input (e.g. PLC)</li> <li>Power supply</li> </ol>			
	3 Transmitter: Observe input values			
Potential equalization	Requirements			
-	No special measures for potential equalization are required.			
Terminals	Tropomittor			
Terminais	<b>Transmitter</b> Spring terminals for wire cross-sections0.5 to 2.5 mm <sup>2</sup> (20 to 14 AWG)			
Cable entries	<ul> <li>Cable gland: M20 × 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in)</li> <li>Thread for cable entry:</li> <li>M20</li> <li>G <sup>1</sup>/<sub>2</sub>"</li> <li>NPT <sup>1</sup>/<sub>2</sub>"</li> </ul>			
Cable specification	Permitted temperature range			
	<ul><li>The installation guidelines that apply in the country of installation must be observed.</li><li>The cables must be suitable for the minimum and maximum temperatures to be expected.</li></ul>			
	Power supply cable (incl. conductor for the inner ground terminal)			
	Standard installation cable is sufficient.			
	Signal cable			
	Current output 4 to 20 mA HART			
	A shielded cable is recommended. Observe grounding concept of the plant.			
	Pulse/frequency/switch output			
	Standard installation cable is sufficient.			
	Performance characteristics			
reference operating conditions	<ul> <li>Error limits following DIN EN 29104, in future ISO 20456</li> <li>Water with +15 to +45 °C (+59 to +113 °F) at2 to 6 bar (29 to 87 psi)</li> <li>Data as indicated in the calibration protocol</li> <li>Accuracy based on accredited calibration rigs according to ISO 17025</li> </ul>			
Maximum measured error	Error limits under reference operating conditions			

Fluctuations in the supply voltage do not have any effect within the specified range.
 Temperature accuracy: ±2 °C (±3.8 °F)

#### Volume flow (standard)


Order code for "Calibration flow":

- Option A "0.5%"
- Option D "0.5%, 3-point, traceable to ISO/IEC 17025"
- Option M "0.5%, 3-point"

#### Measured error

- v > 0.5 m/s (1.64 ft/s): ±0.5 % o.r. ±0.02 % o.f.s.
- $v \le 0.5 \text{ m/s} (1.64 \text{ ft/s}): \pm 0.07 \% \text{ o.f.s.}$
- of full scale value: 5 m/s (16.4 ft/s)

o.r. = of reading; o.f.s. = of full scale value



■ 6 Maximum measured error in % o.r.


Volume flow (EN 1434)

Order code for "Calibration flow": Option Q "2.0% as per EN 1434"

#### Measured error as per EN 1434 Class 2 [%]

 $\pm(2 + 0.02 * q_p/q)$ , limited to  $\pm 5 \%$ 

 $q_p$  = specified continuous flow rate dependent on nominal diameter  $\rightarrow$  🗎 5; q = current flow rate



Error curve as per EN 1434

- *q*<sub>i</sub> Minimum flow rate
- q<sub>p</sub> Permanent flow rate
- *q<sub>s</sub>* Maximum flow rate

#### Accuracy of outputs


-

The output accuracy must be factored into the measured error if analog outputs are used, .

The outputs have the following base accuracy specifications.

	Current output				
	Accuracy	Max. ±5 µA			
	<i>Pulse/frequency output</i> o.r. = of reading				
	Accuracy	Max. ±50 ppm o.r. (over the entire ambient temperature range)			
Repeatability	o.r. = of reading				
	<b>Volume flow</b> ±0.1 % o.r.				
Influence of ambient	Current output				
temperature	o.r. = of reading				
	Temperature coefficient	Max. ±0.005 % o.r./°C			
	Pulse/frequency output				
	Temperature coefficient	No additional effect. Included in accuracy.			


# Installation



#### Orientation

The direction of the arrow on the nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).


Install the measuring device in a parallel plane free of external mechanical stress.
 The internal diameter of the pipe must match the internal diameter of the sensor .



	Orientatio	n	Compact version
A	Vertical orientation	A0015545	
В	Horizontal orientation, transmitter head up	2 A0015589	
С	Horizontal orientation, transmitter head down	A0015590	
D	Horizontal orientation, transmitter head at side	A0015592	×

#### Inlet and outlet runs

If possible, the sensor should be installed downstream from valves, T-pieces, pumps etc. To attain the specified level of accuracy of the measuring device, the below mentioned inlet and outlet runs must be maintained at minimum. If there are several flow disturbances present, the longest specified inlet run must be maintained.




8 Minimum inlet and outlet runs with various flow obstructions

- 1 90° elbow or T-section
- 2 Pump
- 3  $2 \times 90^{\circ}$  elbow, 3-dimensional
- 4 Control valve

#### Outlet runs when installing external devices

If installing an external device, observe the specified distance.




PT Pressure measuring device

# Environment

Ambient temperature range	Transmitter	-25 to +60 °C (-13 to +140 °F)				
	Local display	-20 to $+60$ °C ( $-4$ to $+140$ °F), the readability of the display may be impaired at temperatures outside the temperature range.				
	Sensor	-25 to +60 °C (-13 to +140 °F)				
	<ul> <li>If operating outdoors: Avoid direct sunlight, particularly in warm climatic regions.</li> </ul>					
Storage temperature	All components apart from -50 to +80 °C (-58 to +17	n display modules: '6 °F), preferably at +20 °C (+68 °F)				
Degree of protection	<ul> <li>Transmitter and sensor</li> <li>As standard: IP66/67, type 4X enclosure</li> <li>When housing is open: IP20, type 1 enclosure</li> </ul>					
Shock resistance	Shock due to rough handli	ng following IEC 60068-2-31				
Vibration resistance	<ul> <li>Oscillation, sinusoidal, fe</li> <li>2 to 8.4 Hz, 3.5 mm p</li> <li>8.4 to 500 Hz, 1 g pea</li> <li>Oscillation, broadband m</li> <li>10 to 200 Hz, 0.003 g</li> <li>200 to 2 000 Hz, 0.00</li> <li>Total: 1.54 g rms</li> </ul>	eak ak noise following IEC 60068-2-64 J <sup>2</sup> /Hz				
Electromagnetic compatibility (EMC)	<ul> <li>Complies with emission</li> </ul>	, IEC/EN 61326-2-3 and NAMUR Recommendation 21 (NE 21) limits for industry as per EN 55011 (Class A) in the Declaration of Conformity.				

# Process


Medium temperature range	Sensor
	+0 to +150 °C (+32 to +302 °F)
Sound velocity range	1200 to 2000 m/s (3937 to 6562 ft/s)
Pressure-temperature ratings	The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.
	<ul> <li>Process connections with carbon steel flange material are subject to the following minimum process temperatures:</li> <li>As per EN 1092: -10 °C (+14 °F)</li> <li>As per ASME: -29 °C (-20 °F)</li> </ul>



Smooth flange DIN EN 1092-1Type 01Shape B1, PN 16/25/40


With flange material 1.4571 (316Ti)

#### Slip-on flange following ASME B16.5, class 150





■ 10 With flange material 1.4404 (F316L)


#### Lap joint flange DIN EN 1092-1Type 02Shape A, PN 16




■ 11 With flange material 1.0038 (S235JR); minimum process temperature  $\rightarrow \cong 18$ 









■ 13 With flange material A105; minimum process temperature  $\rightarrow$  ■ 18



🖻 14 With flange material 1.4404 (F316L)



#### Lap joint flange, stamped plate following EN 1092-1(DIN 2501), PN 10




Flow limit

Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.

For an overview of the full scale values for the measuring range, see the "Measuring range" section  $\rightarrow \cong 5$ 

• The minimum recommended full scale value is approx. 1/20 of the maximum full scale value.

• In most applications, 10 to 50 % of the maximum full scale value can be considered ideal.



■ 16 Pressure loss DN 50 to 150 (2 to 6")


To calculate the pressure loss, use the *Applicator* sizing tool  $\rightarrow \square 34$ 

System pressure

It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas. This is prevented by means of a sufficiently high system pressure.


For this reason, the following mounting locations are recommended:

- At the lowest point in a vertical pipe
- Downstream from pumps (no danger of vacuum)




#### Thermal insulation

In the case of some fluids, it is important to keep the heat radiated from the sensor to the transmitter to a low level. A wide range of materials can be used for the required insulation.



- t Maximum insulation thickness 2 cm (0.79 in)
- Minimum distance from transmitter to insulation а

# Mechanical construction



#### Order code for "Housing", options A "Compact, aluminum, coated"

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E <sup>1)</sup> [mm]	F <sup>1)</sup> [mm]	G [mm]	K <sup>2)</sup> [mm]	L [mm]	M [mm]
50	136	82	54	82.5	233.5	316	136	35	3)	61.5
65	136	82	54	92.5	238	330.5	136	43.8	3)	71
80	136	82	54	100	241	341	136	49.3	3)	76.5
100	136	82	54	117.5	258.5	376	136	75	3)	110
150	136	82	54	150	276.5	426.5	136	110.3	3)	145

When using a display (order code for "Display; operation", option B): Values +28 mm 1)

Tolerance: ±2 mm

2) 3) Dependent on respective process connection

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F <sup>1)</sup> [mm]	G [mm]	K <sup>2)</sup> [mm]	L [mm]	M [mm]
50	137	77	60	82.5	228.5	311	133.5	35	3)	61.5
65	137	77	60	92.5	233	325.5	133.5	43.8	3)	71
80	137	77	60	100	236	336	133.5	49.3	3)	76.5
100	137	77	60	117.5	253.5	371	133.5	75	3)	110
150	137	77	60	150	271.5	421.5	133.5	110.3	3)	145

Order code for "Housing", Option D "Compact, stainless"


1) When using a display (order code for "Display; operation", option B): Values +15.5 mm

2) Tolerance: ±2 mm

3) Depends on the process connection in question

#### Flange connections

Fixed flange



#### Smooth flange DIN EN 1092-1 Type 01 Form B1, PN 16/25/40 1.4571 (316Ti): order code for "Process connection", option D51, D52, D53

DN [mm]	Pressure rating PN	A [mm]	B [mm]	C [mm]	D [mm]	E <sup>1)</sup> [mm]	L [mm]
50	40	165	125	4 × 18	20	56.3	300 <sup>2)</sup>
65	16/25	185	145	8 × 18	20/22	72.1	300 <sup>2)</sup>
80	16/25	200	160	8 × 18	20/24	84.5	350 <sup>3)</sup>
100	16/25	220/235	180/190	8 × 18/22	22/26	110.3	350 <sup>3)</sup>
150	16/25	285/300	240/250	8 × 22/26	24/30	164.3	500 <sup>3)</sup>

1) Tolerance: ±2 mm

2) Tolerance: 0/-2 mm

3) Tolerance: 0/-3 mm

#### Slip-on flange following ASME B16.5: Class 150 1.4404 (F316L): order code for "Process connection", option A1S DN Α В С D E 1) L [mm] [mm] [mm] [mm] [mm] [mm] [mm] 300<sup>2)</sup> 50 152.4 120.7 $4 \times 19.1$ 25.4 56.3 190.5 152.4 4 × 19.1 30.2 350 <sup>3)</sup> 80 84.5


Slip-on flange following ASME B16.5: Class 150 1.4404 (F316L): order code for "Process connection", option A1S									
DN         A         B         C         D         E <sup>1)</sup> L           [mm]         [mm]         [mm]         [mm]         [mm]         [mm]									
100	228.6	190.5	8 × 19.1	33.3	110.3	350 <sup>3)</sup>			
150	279.4	241.3	8×22.4	39.6	164.3	500 <sup>3)</sup>			

Tolerance: ±2 mm 1)

2) Tolerance: 0/-2 mm

3) Tolerance: 0/-3 mm

Lap joint flange



Lap joint flange DIN EN 1092-1 Type 02 Form A: PN 16
1.0038 (S235JR): order code for "Process connection", option D32
1.4306 (F304L), 1.4307 (F304L): order code for "Process connection", option D34

DN A [mm] [mm]		B [mm]	C [mm]	D [mm]	L [mm]
50	165	125	20	4 × 18	300 <sup>1)</sup>
65	185	145	20	8 × 18	300 <sup>1)</sup>
80	200	160	20	8 × 18	350 <sup>2)</sup>
100	220	180	22	8 × 18	350 <sup>2)</sup>
150	285	240	24	8 × 22	500 <sup>2)</sup>

Tolerance: 0/-2 mm 1)

2) Tolerance: 0/-3 mm

Lap joint flange following ASME B16.5: Class 150


A105: order code for "Process connection", option A12 1.4404 (F316L): order code for "Process connection", option A14

DN [mm]	A [mm]	B C [mm] [mm]		D [mm]	L [mm]
50	152.4	120.7	25.4	4 × 19.1	300 <sup>1)</sup>
80	190.5	152.4	30.2	4 × 19.1	350 <sup>2)</sup>
100	228.6	190.5	33.3	8 × 19.1	350 <sup>2)</sup>
150	279.4	241.3	39.6	8×22.4	500 <sup>2)</sup>

Tolerance: 0/-2 mm 1)

2) Tolerance: 0/-3 mm

#### Lap joint flange, stamped plate



# Lap joint flange, stamped plate following EN 1092-1 (DIN 2501): PN 10 1.0038 (S235JR): order code for "Process connection", option D21

1.4301 (F304): order code for "Process connection", option D23


DN [mm]			C [mm]	D [mm]	L [mm]
50	165	125	18.5	4 × 17.5	300 <sup>1)</sup>
65	185	145	20.0	4 × 17.5	300 <sup>1)</sup>
80	200	160	23.5	8 × 17.5	350 <sup>2)</sup>
100	220	180	24.5	8 × 17.5	350 <sup>2)</sup>
150	285	240	25.0	8 × 21.5	500 <sup>2)</sup>

1) Tolerance: 0/-2 mm

2) Tolerance: 0/-3 mm

#### Dimensions in US units

#### **Compact version**



Order code for "Housing", options A "Compact, aluminum, coated"

DN [in]	A [in]	B [in]	C [in]	D [in]	E <sup>1)</sup> [in]	F <sup>1)</sup> [in]	G [in]	K <sup>2)</sup> [in]	L [in]	M [in]
2	5.35	3.23	2.13	3.25	9.19	12.4	5.35	1.38	3)	2.42
2 1⁄2	5.35	3.23	2.13	3.64	9.37	13.0	5.35	1.72	3)	2.80
3	5.35	3.23	2.13	3.94	9.49	13.4	5.35	1.94	3)	3.01

DN [in]	A [in]	B [in]	C [in]	D [in]	E <sup>1)</sup> [in]	F <sup>1)</sup> [in]	G [in]	K <sup>2)</sup> [in]	L [in]	M [in]
4	5.35	3.23	2.13	4.63	10.2	14.8	5.35	2.95	3)	4.33
6	5.35	3.23	2.13	5.91	10.9	16.8	5.35	4.34	3)	5.71

1) When using a display (order code for "Display; operation", option B): Values +1.1 in

2) Tolerance: ±0.08 in

3) Depends on the process connection in question

Order code	for "Housing"	Option D "Compact,	stainloss"
Under Loue	joi mousing,	option D Compact,	Stuttiess

DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F <sup>1)</sup> [in]	G [in]	K <sup>2)</sup> [in]	L [in]	M [in]
2	5.4	3.03	2.36	3.25	8.98	12.24	5.24	1.38	3)	2.42
2 1/2	5.4	3.03	2.36	3.64	9.17	12.80	5.24	1.72	3)	2.80
3	5.4	3.03	2.36	3.94	9.30	13.22	5.24	1.94	3)	3.01
4	5.4	3.03	2.36	4.63	9.96	14.60	5.24	2.95	3)	4.33
6	5.4	3.03	2.36	5.91	10.67	16.57	5.24	4.34	3)	5.71


When using a display (order code for "Display; operation", option B): Values +0.60 in Tolerance:  $\pm 0.08$  in

1) 2)

3) Depends on the process connection in question

#### Flange connections

Fixed flange




Slip-on flange following ASME B16.5: Class 150 1.4404 (F316L): order code for "Process connection", option A1S									
DN [in]	A [in]	B [in]	C [in]	D [in]	E <sup>1)</sup> [in]	L [in]			
2	6.00	4.75	4 × 0.75	1.00	2.22	11.8 <sup>2)</sup>			
3	7.50	6.00	4 × 0.75	1.19	3.33	13.8 <sup>3)</sup>			
4	9.00	7.50	8 × 0.75	1.31	4.34	13.8 <sup>3)</sup>			
6	11.0	9.50	8 × 0.88	1.56	6.47	19.7 <sup>3)</sup>			

Tolerance: ±0.08 in 1)

2) Tolerance: 0/-0.08 in

3) Tolerance: 0/-0.12 in

#### Lap joint flange



# Lap joint flange following ASME B16.5: Class 150 A105: order code for "Process connection", option A12

1.4404 (F316L): order code for "Process connection", option A14

DN [in]	A [in]	B [in]	C [in]	D [in]	L [in]
2	6.00	4.75	1.00	4 × 0.75	11.8 <sup>1)</sup>
3	7.50	6.00	1.19	4 × 0.75	13.8 <sup>2)</sup>
4	9.00	7.50	1.31	8 × 0.75	13.8 <sup>2)</sup>
6	11.0	9.50	1.56	8 × 0.88	19.7 <sup>2)</sup>

Tolerance: 0/-0.08 in 1)

2) Tolerance: 0/-0.12 in

Weight

#### Weight in SI units

#### Compact version

	Order code	for "Housing",	option A	"Compact,	aluminum,	coated"
--	------------	----------------	----------	-----------	-----------	---------

Nominal diameter [mm]	Version	Fixed flange		Lap joint flar	Lap joint flange, stamped plate	
		EN 1092-1 (DIN 2501) <sup>1)</sup> [kg]	ASME B16.5 <sup>2)</sup> [kg]	EN 1092-1 (DIN 2501) <sup>3)</sup> [kg]	ASME B16.5 <sup>2)</sup> [kg]	EN 1092-1 (DIN 2501) <sup>4)</sup> [kg]
50	Single-path	9.63	8.43	9.35	8.55	7.65
65	Single-path	11.26	-	11.18	-	8.52
80	Single-path	12.68	13.28	12.66	13.36	9.23
100	Two-path	16.55	18.55	16.40	18.33	11.65
150	Two-path	25.85	26.85	22.45	26.67	17.95

1) Pressure rating PN 40 (DN 50), PN 16 (DN 65 to 150)

Pressure rating, class 150 2)

Pressure rating PN 10/16 Pressure rating PN 10 3)

4)

#### Order code for "Housing", Option D "Compact, stainless"

Nominal diameter [mm]	Version	Fixed flange		Lap joint flan	Lap joint flange, stamped plate	
		EN 1092-1 (DIN 2501) <sup>1)</sup> [kg]	ASME B16.5 <sup>2)</sup> [kg]	EN 1092-1 (DIN 2501) <sup>3)</sup> [kg]	ASME B16.5 [kg]	EN 1092-1 (DIN 2501) <sup>4)</sup> [kg]
50	Single-path	9.44	8.24	9.16	8.36	7.46
65	Single-path	11.07	-	10.99	-	8.33
80	Single-path	12.49	13.09	12.47	13.17	9.04
100	Two-path	16.36	18.36	16.22	18.14	11.46
150	Two-path	25.66	26.66	22.26	26.48	17.76

1) Pressure rating PN 40 (DN 50), PN 16 (DN 65 to 150)

2) Pressure rating, class 150

3) Pressure rating PN 10/16

4) Pressure rating PN 10

#### Weight in US units

#### Compact version

#### Order code for "Housing", option A "Compact, aluminum, coated"

Nominal diameter [in]	Version	Fixed flange ASME B16.5 <sup>1)</sup> [lbs]	Lap joint flange ASME B16.5 <sup>1)</sup> [lbs]
2	Single-path	17.64	17.63
3	Single-path	28.66	28.66
4	Two-path	39.68	39.68
6	Two-path	57.32	57.32

1) Pressure rating, class 150

#### Order code for "Housing", Option D "Compact, stainless"

Nominal diameter	Version	Fixed flange	Lap joint flange
[in]		ASME B16.5 <sup>1)</sup> [lbs]	ASME B16.5 [lbs]
2	Single-path	17.63	17.63
3	Single-path	28.66	28.66
4	Two-path	39.68	39.68
6	Two-path	57.32	57.32


1) Pressure rating, class 150

Materials

#### Transmitter housing

- Order code for "Housing", option A "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
- Order code for "Housing", option D "Compact, stainless": Stainless steel 1.4301 (304)
- Window material for optional local display (→ 
   <sup>B</sup> 30): Order code for "Display; Operation", option B: glass

#### Cable entries/cable glands



#### 🖻 17 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland  $M20 \times 1.5$
- 3 Adapter for cable entry with female thread G  $\frac{1}{2}$  or NPT  $\frac{1}{2}$

#### Order code for "Housing", option A "Compact, aluminum, coated"

Cable entry/cable gland	Material
Cable gland M20 × 1.5	
Adapter for cable entry with female thread G <sup>1</sup> /2"	Nickel-plated brass
Adapter for cable entry with female thread NPT ½"	

#### Order code for "Housing", option D "Compact, stainless"

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Stainless steel, 1.4404 (316L)
Adapter for cable entry with female thread G <sup>1</sup> /2"	
Adapter for cable entry with female thread NPT ½"	

#### Sensor housing

Stainless steel (cold worked):

- 1.4301 (304)
- 1.4301 (304)

#### **Process connections**

- Stainless steel:
  - 1.4301 (304)
  - 1.4306 (304L)
  - 1.4404 (316L)
- 1.4571 (316Ti)
- Steel S235JR (1.0038)
   Carbon stack A105
- Carbon steel A105

Available process connections→ 🗎 29

**Process connections** 


Flanges: • EN 1092-1 (DIN 2501)

- ASME B16.5


For information on the different materials used in the process connections  $\rightarrow$   $\cong$  29

Operating concept	Operator-oriented menu structure for user-specific tasks <ul> <li>Commissioning</li> <li>Operation</li> <li>Diagnostics</li> <li>Expert level</li> </ul>		
	<ul> <li>Quick and safe commissioning</li> <li>Individual menus for applications</li> <li>Menu guidance with brief explanations of the individual parameter functions</li> </ul>		
	<ul> <li>Reliable operation</li> <li>Operation in the following languages: <ul> <li>Via "FieldCare", "DeviceCare" operating tool:</li> <li>English, German, French, Spanish, Italian, Chinese, Japanese</li> </ul> </li> <li>Via integrated Web browser: <ul> <li>English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech, Swedish, Korean</li> </ul> </li> <li>Uniform operating philosophy applied to operating tools and Web browser</li> <li>If replacing the electronic module, transfer the device configuration via the plug-in memory (HistoROM DAT) which contains the process and measuring device data and the event logbook. No need to reconfigure.</li> </ul>		
	<ul> <li>Efficient diagnostics increase measurement availability</li> <li>Troubleshooting measures can be called up via the operating tools</li> <li>Diverse simulation options</li> <li>Status indicated by several light emitting diodes (LEDs) on the electronic module in the housing compartment</li> </ul>		
Local display	The local display is only available with the following device order code: Order code for "Display; operation", option <b>B</b> : 4-line; illuminated, via communication		
	<ul> <li>Display element <ul> <li>4-line liquid crystal display with 16 characters per line.</li> <li>White background lighting; switches to red in event of device errors.</li> <li>Format for displaying measured variables and status variables can be individually configured.</li> <li>Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F). The readability of the display may be impaired at temperatures outside the temperature range.</li> </ul> </li> </ul>		

# Human interface



#### Via HART protocol




I8 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 Field Xpert SMT70
- 7 VIATOR Bluetooth modem with connecting cable
- 8 Transmitter

#### Service interface

Via service interface (CDI-RJ45)

HART



- 🗉 19 Connection for the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output
- 1 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

### **Certificates and approvals**

Currently available certificates and approvals can be called up via the product configurator.

CE mark	The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.		
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.		
RCM-tick symbol	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".		
HART certification	HART interface		
	<ul> <li>The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:</li> <li>Certified according to HART 7.5</li> <li>The device can also be operated with certified devices of other manufacturers (interoperability)</li> </ul>		
Pressure Equipment Directive	The devices can be ordered with or without a PED approval. If a device with a PED approval is required, this must be explicitly stated in the order.		
	<ul> <li>With the identification PED/G1/x (x = category) on the sensor nameplate, Endress+Hauser confirms conformity with the "Essential Safety Requirements" specified in Appendix I of the Pressure Equipment Directive 2014/68/EU.</li> <li>Devices bearing this marking (PED) are suitable for the following types of medium: Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to0.5 bar (7.3 psi)</li> <li>Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Article 4 paragraph 3 of the Pressure Equipment Directive 2014/68/EU. The range of application is indicated in tables 6 to 9 in Annex of the Pressure Equipment Directive 2014/68/EU.</li> </ul>		

Other standards and guidelines

#### EN 60529

Degrees of protection provided by enclosures (IP code)

- EN 61010-1 Safety requirements for electrical equipment for measurement, control and laboratory use -
- general requirements IEC/EN 61326 Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC
- requirements).NAMUR NE 21
- Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment • NAMUR NE 32
- Data retention in the event of a power failure in field and control instruments with microprocessors
- NAMUR NE 43 Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.
- NAMUR NE 53
- Software of field devices and signal-processing devices with digital electronics NAMUR NE 80
- The application of the pressure equipment directive to process control devices
- NAMUR NE 105
- Specifications for integrating fieldbus devices in engineering tools for field devices
- NAMUR NE 107
  - Self-monitoring and diagnosis of field devices
- NAMUR NE 131 Requirements for field devices for standard applications

# Ordering information

Detailed ordering information is available as follows:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
   -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
   Open product page -> The "Configure" button to the right of the product image opens the Product
   Configurator.
- From your Endress+Hauser Sales Center:www.addresses.endress.com

#### Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

# Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.



Detailed information on the application packages:

Heartbeat Technology	Package	Description
	Heartbeat Verification +Monitoring	<ul> <li>Heartbeat Verification</li> <li>Meets the requirement for traceable verification to DIN ISO 9001:2008</li> <li>Chapter 7.6 a) "Control of monitoring and measuring equipment".</li> <li>Functional testing in the installed state without interrupting the process.</li> <li>Traceable verification results on request, including a report.</li> <li>Simple testing process via local operation or other operating interfaces.</li> <li>Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.</li> <li>Extension of calibration intervals according to operator's risk assessment.</li> </ul>
		<ul> <li>Heartbeat Monitoring</li> <li>Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to:</li> <li>Draw conclusions - using these data and other information - about the impact the measuring application has on the measuring performance over time.</li> <li>Schedule servicing in time.</li> <li>Monitor the process or product quality, e.g. gas pockets.</li> </ul>

# Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Communication-specific	Accessories	Description
accessories	Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface.           Image: Technical Information TI00404F
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. Technical Information TI405C/07
	HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.
	Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. Operating Instructions BA00061S
	Fieldgate FXA42	Is used to transmit the measured values of connected 4 to 20 mA analog measuring devices, as well as digital measuring devices • Technical Information TI01297S • Operating Instructions BA01778S • Product page: www.endress.com/fxa42

Field Xpert SMT70	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress.         This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.         Image: Technical Information TI01342S         Operating Instructions BA01709S         Product page: www.endress.com/smt70
Field Xpert SMT77	The Field Xpert SMT77 tablet PC for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1.
	<ul> <li>Technical Information TI01418S</li> <li>Operating Instructions BA01923S</li> <li>Product page: www.endress.com/smt77</li> </ul>

Service-specific accessories	Accessories	Description
	Applicator	<ul> <li>Software for selecting and sizing Endress+Hauser measuring devices:</li> <li>Choice of measuring devices for industrial requirements</li> <li>Calculation of all the necessary data for identifying the optimum flowmeter: <ul> <li>e.g. nominal diameter, pressure loss, flow velocity and accuracy.</li> <li>Graphic illustration of the calculation results</li> <li>Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.</li> </ul> </li> </ul>
		<ul><li>Applicator is available:</li><li>Via the Internet: https://portal.endress.com/webapp/applicator</li><li>As a downloadable DVD for local PC installation.</li></ul>
	W@M	W@M Life Cycle ManagementImproved productivity with information at your fingertips. Data relevant to aplant and its components is generated from the first stages of planning andduring the asset's complete life cycle.W@M Life Cycle Management is an open and flexible information platformwith online and on-site tools. Instant access for your staff to current, in-depthdata shortens your plant's engineering time, speeds up procurement processesand increases plant uptime.Combined with the right services, W@M Life Cycle Management boostsproductivity in every phase. For more information, visitwww.endress.com/lifecyclemanagement
	FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.
	DeviceCare	Operating Instructions BA00027S and BA00059S
	DeviceCare	Tool to connect and configure Endress+Hauser field devices.

System	components
--------	------------

Accessories	Description
Memograph M graphic data manager	<ul> <li>The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.</li> <li>Technical Information TI00133R</li> <li>Operating Instructions BA00247R</li> </ul>

# Supplementary documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

 W@M Device Viewer (www.endress.com/deviceviewer): Enter the serial number from nameplate

• *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2D matrix code (QR code) on the nameplate

#### Standard documentation Brief Operating Instructions

Brief Operating Instructions for the sensor

Measuring device	Documentation code
Proline Prosonic Flow E	KA01329D

#### Brief Operating Instructions for transmitter

Measuring device	Documentation code
	HART
Proline 100	KA01330D

#### **Operating Instructions**

Measuring device	Documentation code
	HART
Prosonic Flow E 100	BA01769D

#### **Description of Device Parameters**

Measuring device	Documentation code HART
Prosonic Flow 100	GP01124D

#### Supplementary devicedependent documentation

#### Special documentation

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01614D
RFID TAG	SD01565D

Contents	Documentation code HART
Heartbeat Technology	SD02079D

#### Installation Instructions

Contents	Comment
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory .

# **Registered trademarks**

HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

www.addresses.endress.com

