# Technical Information **Proline Promass I 100**

Coriolis flowmeter

**Products** 



# Combines in-line viscosity and flow measurement with an ultra-compact transmitter

# Application

- Measuring principle operates independently of physical fluid properties such as viscosity or density
- Liquid and gas measurement in applications requiring low pressure loss and sensitive handling of the medium

# Device properties

- Straight, easy-to-clean single-tube system
- TMB® technology
- Titanium measuring tube
- Robust, ultra-compact transmitter housing
- Highest degree of protection: IP69K
- Local display available

# Your benefits

- Energy-saving full bore design enables minimal pressure loss
- Fewer process measuring points multivariable measurement (flow, density, temperature)
- Space-saving installation no inlet/outlet run needs
- Space-saving transmitter full functionality on smallest footprint
- Time-saving local operation without additional software and hardware – integrated web server
- Integrated verification Heartbeat Technology $^{TM}$



# Table of contents

<b>Document information</b>		Vibration resistance	52
Function and system design			
Measuring principle	. 5		52
Measuring system	. 5	Electromagnetic compatibility (EMC)	2۷
Equipment architecture			
Safety		Process	52
		Medium temperature range	52
Toward			
Input		Pressure-temperature ratings	53
Measured variable		• •	56
Measuring range		Flow limit	57
Operable flow range		Pressure loss	57
Input signal	9	System pressure	57
		Thermal insulation	57
Output	10		
Output signal	10	Vibrations	58
Signal on alarm			
Ex connection data	13		-0
Low flow cut off	14		59
Galvanic isolation	14		
Protocol-specific data		Dimensions in US units	
Trococor opecane data	**		
_		Materials	
Power supply	24	Process connections	
Terminal assignment		Surface roughness	82
Pin assignment, device plug $\dots$			
Supply voltage	33	Operability	82
Power consumption	34	Operating concept	
Current consumption	34	Local display	
Power supply failure	34	Remote operation	
Electrical connection	35	Service interface	
Potential equalization	40	Service interrace	04
Terminals	40		
Cable entries	40	Certificates and approvals	
Cable specification	40	CE mark	
		C-Tick symbol	
Performance characteristics	42	Ex approval	
Reference operating conditions	1	Sanitary compatibility	
Maximum measured error		HART certification	
	44	Certification PROFIBUS	88
Repeatability	44	Certification PROFINET	88
Response time	44	EtherNet/IP certification	88
*		Modbus RS485 certification	88
Influence of medium temperature		Pressure Equipment Directive	88
Influence of medium pressure	45	Other standards and guidelines	89
Design fundamentals	45		
		Ordering information	QQ
Installation		Ordering information	0,
Mounting location	46		
Orientation	47		89
Inlet and outlet runs	48	3,	90
Special mounting instructions	48	Concentration	
Mounting Safety Barrier Promass 100	49	Viscosity	90
<b>.</b>	, ,	Aggagaging	01
			91
Ambient temperature range	49	Device-specific accessories	91
Storage temperature	51	Communication-specific accessories	
Climate class	51	Service-specific accessories	92

2

System components	92
Supplementary documentation	93
Registered trademarks	93

# **Document information**

# Symbols used

# **Electrical symbols**

Symbol	Meaning	Symbol	Meaning
	Direct current	~	Alternating current
≂	Direct current and alternating current	≐	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Protective ground connection A terminal which must be connected to ground prior to establishing any other connections.	\$	Equipotential connection A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice.

# Symbols for certain types of information

Symbol	Meaning
$\checkmark$	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
X	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
[i	Reference to documentation
A	Reference to page
	Reference to graphic
	Visual inspection

# Symbols in graphics

Symbol	Meaning	Symbol	Meaning
1, 2, 3,	Item numbers	1. , 2. , 3	Series of steps
A, B, C,	Views	A-A, B-B, C-C,	Sections
EX	Hazardous area	×	Safe area (non-hazardous area)
≋➡	Flow direction		

# Function and system design

### Measuring principle

The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present in a system when both translational and rotational movements are superimposed.

 $F_c = 2 \cdot \Delta m (v \cdot \omega)$ 

 $F_c$  = Coriolis force

 $\Delta m = moving mass$ 


 $\omega = rotational velocity$ 

v = radial velocity in rotating or oscillating system

The amplitude of the Coriolis force depends on the moving mass  $\Delta m$ , its velocity v in the system and thus on the mass flow. Instead of a constant rotational velocity  $\omega$ , the sensor uses oscillation.

In the sensor, an oscillation is produced in the measuring tube. The Coriolis forces produced at the measuring tube cause a phase shift in the tube oscillations (see illustration):

- If there is zero flow (i.e. when the fluid stands still), the oscillation measured at points A and B has the same phase (no phase difference).
- Mass flow causes deceleration of the oscillation at the inlet of the tubes (2) and acceleration at the outlet (3).



A0016772

The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube oscillations at the inlet and outlet. System balance is created by exciting an eccentrically arranged swinging mass to antiphase oscillation. The measuring principle operates independently of temperature, pressure, viscosity, conductivity and flow profile.

# Density measurement

The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising measuring tube and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. Resonance frequency is thus a function of medium density. The microprocessor utilizes this relationship to obtain a density signal.

# Volume measurement

Together with the measured mass flow, this is used to calculate the volume flow.

### Temperature measurement

The temperature of the measuring tube is determined in order to calculate the compensation factor due to temperature effects. This signal corresponds to the process temperature and is also available as an output signal.


# Measuring system

The device consists of a transmitter and a sensor. If a device with Modbus RS485 intrinsically safe is ordered, the Safety Barrier Promass 100 is part of the scope of supply and must be implemented to operate the device.

The device is available as a compact version:

The transmitter and sensor form a mechanical unit.

# Transmitter



Device versions and materials:

- Compact, aluminum coated:
   Aluminum, AlSi10Mg, coated
- Compact, hygienic, stainless:
   Hygienic version, stainless steel 1.4301 (304)
- Ultra-compact, hygienic, stainless:
   Hygienic version, stainless steel 1.4301 (304)


### Configuration:

- Via operating tools (e.g. FieldCare)
- Additionally for device version with local display:
   Via Web browser (e.g. Microsoft Internet Explorer)
- Also for device version with 4-20 mA HART, pulse/frequency/switch output:

Via Web browser (e.g. Microsoft Internet Explorer)


- Also for device version with EtherNet/IP output:
  - Via Web browser (e.g. Microsoft Internet Explorer)
  - Via Add-on Profile Level 3 for automation system from Rockwell Automation
  - Via Electronic Data Sheet (EDS)
- Also for device version with PROFINET output:
- Via Web browser (e.g. Microsoft Internet Explorer)
- Via device master file (GSD)

### Sensor




- Sensitive fluid handling thanks to straight single-tube system
- Simultaneous measurement of viscosity, flow, volume flow, density and temperature (multivariable)
- Immune to process influences
- Nominal diameter range: DN 8 to 80 (3/8 to 3")
- Materials:
  - Sensor: stainless steel, 1.4301/1.4307 (304L)
  - Measuring tubes: titanium Grade 9
  - Process connections: stainless steel, 1.4301 (304), wetted parts: titanium Grade 2

# Safety Barrier Promass 100



- Dual-channel safety barrier for installation in non-hazardous locations or zone 2/div. 2:
  - Channel 1: DC 24 V power supply
  - Channel 2: Modbus RS485
- In addition to current, voltage and power limitation, it offers galvanic isolation of circuits for explosion protection.
- Easy top-hat rail mounting (DIN 35 mm) for installation in control cabinets

# Equipment architecture



 $\ \blacksquare \ 1$  Possibilities for integrating measuring devices into a system

- 1 Automation system (e.g. PLC)
- 2 EtherNet/IP
- 3 PROFIBUS DP
- 4 Modbus RS485
- 5 4-20 mA HART, pulse/frequency/switch output
- 6 Safety Barrier Promass 100
- 7 Modbus RS485 intrinsically safe
- 8 Non-hazardous area
- 9 Non-hazardous area and Zone 2/Div. 2
- 10 Intrinsically safe area and Zone 1/Div. 1

# Safety

# IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

# Input

# Measured variable

# Direct measured variables

- Mass flow
- Density
- Temperature
- Viscosity

# Calculated measured variables

- Volume flow
- Corrected volume flow
- Reference density

# Measuring range

# Measuring ranges for liquids

D	N	Measuring range full scal	e values $\dot{m}_{\min(F)}$ to $\dot{m}_{\max(F)}$
[mm]	[in]	[kg/h]	[lb/min]
8	3/8	0 to 2 000	0 to 73.50
15	1/2	0 to 6 500	0 to 238.9
15 FB	⅓ FB	0 to 18 000	0 to 661.5
25	1	0 to 18 000	0 to 661.5
25 FB	1 FB	0 to 45 000	0 to 1654
40	1½	0 to 45 000	0 to 1654
40 FB	1½ FB	0 to 70 000	0 to 2 573
50	2	0 to 70 000	0 to 2 573
50 FB	2 FB	0 to 180 000	0 to 6615
80	3	0 to 180 000	0 to 6615
FB = Full bore			

# Measuring ranges for gases

The full scale values depend on the density of the gas and can be calculated with the formula below:  $\dot{m}_{max(G)}=\dot{m}_{max(F)}\cdot\rho_G:x$ 

ṁ <sub>max(G)</sub>	Maximum full scale value for gas [kg/h]
m <sub>max(F)</sub>	Maximum full scale value for liquid [kg/h]
$\dot{m}_{\max(G)} < \dot{m}_{\max(F)}$	$\dot{m}_{max(G)}$ can never be greater than $\dot{m}_{max(F)}$
$ ho_G$	Gas density in [kg/m³] at operating conditions

DN		х
[mm]	[in]	[kg/m³]
8	3/8	60
15	1/2	80
15 FB	½ FB	90
25	1	90
25 FB	1 FB	90
40	1½	90
40 FB	1½ FB	90

DN		х
[mm]	[in]	[kg/m³]
50	2	90
50 FB	2 FB	110
80	3	110
FB = Full bore		1



To calculate the measuring range, use the *Applicator* sizing tool  $\rightarrow \triangleq 92$ 

# Calculation example for gas

- Sensor: Promass I, DN 50
- Gas: Air with a density of 60.3 kg/m³ (at 20 °C and 50 bar)
- Measuring range (liquid): 70 000 kg/h
- $x = 90 \text{ kg/m}^3 \text{ (for Promass I, DN 50)}$

Maximum possible full scale value:

 $\dot{m}_{max(G)} = \dot{\bar{m}}_{max(F)} \cdot \rho_G : x = 70\,000 \text{ kg/h} \cdot 60.3 \text{ kg/m}^3 : 90 \text{ kg/m}^3 = 46\,900 \text{ kg/h}$ 

# Recommended measuring range

"Flow limit" section  $\rightarrow \triangleq 57$ 

# Operable flow range

Over 1000:1.


Flow rates above the preset full scale value are not overridden by the electronics unit, with the result that the totalizer values are registered correctly.

# Input signal

### External measured values

To increase the accuracy of certain measured variables or to calculate the corrected volume flow for gases, the automation system can continuously write different measured values to the measuring device:

- Operating pressure to increase accuracy (Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S)
- Medium temperature to increase accuracy (e.g. iTEMP)
- Reference density for calculating the corrected volume flow for gases



It is recommended to read in external measured values to calculate the following measured variables:

- Mass flow
- Corrected volume flow

# HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

# Digital communication

The measured values can be written from the automation system to the measuring via:

- PROFIBUS DP
- Modbus RS485
- EtherNet/IP
- PROFINET

# Output

# Output signal

# **Current output**

Current output	4-20 mA HART (active)
Maximum output values	<ul><li>DC 24 V (no flow)</li><li>22.5 mA</li></ul>
Load	$0$ to $700\Omega$
Resolution	0.38 μΑ
Damping	Adjustable: 0.07 to 999 s
Assignable measured variables	<ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>

# Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	■ DC 30 V ■ 25 mA
Voltage drop	For 25 mA: ≤ DC 2 V
Pulse output	
Pulse width	Adjustable: 0.05 to 2 000 ms
Maximum pulse rate	10 000 Impulse/s
Pulse value	Adjustable
Assignable measured variables	<ul><li>Mass flow</li><li>Volume flow</li><li>Corrected volume flow</li></ul>
Frequency output	
Output frequency	Adjustable: 0 to 10 000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	<ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s

Number of switching cycles	Unlimited
Assignable functions	<ul> <li>Off</li> <li>On</li> <li>Diagnostic behavior</li> <li>Limit value</li> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>Totalizer 1-3</li> <li>Flow direction monitoring</li> <li>Status</li> <li>Partially filled pipe detection</li> <li>Low flow cut off</li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>

# PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud

# Modbus RS485

Physical interface	In accordance with EIA/TIA-485-A standard
Terminating resistor	<ul> <li>For device version used in non-hazardous areas or Zone 2/Div. 2: integrated and can be activated via DIP switches on the transmitter electronics module</li> <li>For device version used in intrinsically safe areas: integrated and can be activated via DIP switches on the Safety Barrier Promass 100</li> </ul>

# EtherNet/IP

Standards In accordance with IEEE 802.3	
---	--

# **PROFINET**

Standards	In accordance with IEEE 802.3
-----------	-------------------------------

# Signal on alarm

Depending on the interface, failure information is displayed as follows:

# **Current output**

# 4-20 mA

Failure mode	Choose from:  4 to 20 mA in accordance with NAMUR recommendation NE 43  4 to 20 mA in accordance with US  Min. value: 3.59 mA  Max. value: 22.5 mA  Freely definable value between: 3.59 to 22.5 mA  Actual value  Last valid value
--------------	---

# HART

Device diagnostics	Device condition can be read out via HART Command 48

# Pulse/frequency/switch output

Pulse output	
Failure mode	Choose from:  Actual value No pulses
Frequency output	
Failure mode	Choose from:  Actual value  O Hz  Defined value: 0 to 12 500 Hz
Switch output	
Failure mode	Choose from:  Current status  Open Closed

# PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

# Modbus RS485

Failure mode	Choose from:
	<ul> <li>NaN value instead of current value</li> <li>Last valid value</li> </ul>

# EtherNet/IP

Device diagnostics	Device condition can be read out in Input Assembly
--------------------	--

# **PROFINET**

	T
Device diagnostics	In accordance with "Application Layer protocol for decentral device periphery and
	distributed automation", version 2.3

# Local display

Plain text display	With information on cause and remedial measures
Backlight	Red backlighting indicates a device error.

i

Status signal as per NAMUR recommendation NE 107  $\,$ 

# Operating tool

- Via digital communication:
  - HART protocol
  - PROFIBUS DP
  - Modbus RS485
  - EtherNet/IP
  - PROFINET
- Via service interface
- Via Web server

12

Plain text display	With information on cause and remedial measures



Additional information on remote operation  $\rightarrow~\equiv~83$ 

# Web browser

Plain text display	With information on cause and remedial measures
--------------------	---

# Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes
	The following information is displayed depending on the device version:  Supply voltage active  Data transmission active  Device alarm/error has occurred  EtherNet/IP network available  EtherNet/IP connection established  PROFINET network available  PROFINET onnection established  PROFINET blinking feature

# Ex connection data

These values only apply for the following device version:

Order code for "Output", option M "Modbus RS485", for use in intrinsically safe areas

# Safety Barrier Promass 100

Safety-related values

Terminal numbers			
Supply voltage		Signal tra	nsmission
2 (L-)	1 (L+)	26 (A) 27 (B)	
U <sub>nom</sub> = DC 24 V U <sub>max</sub> = AC 260 V		$U_{\text{nom}} = U_{\text{max}} = A$	DC 5 V AC 260 V

# Intrinsically safe values

Terminal numbers				
	Supply voltage		Signal trai	nsmission
	20 (L-) 10 (L+)		62 (A)	72 (B)
	$\begin{array}{c} U_o=16.24~V\\ I_o=623~mA\\ P_o=2.45~W\\ With~IIC~^{1)}:L_o=92.8~\mu\text{H},~C_o=0.433~\mu\text{F},~L_o/R_o=14.6~\mu\text{H}/\Omega\\ With~IIB~^{1)}:L_o=372~\mu\text{H},~C_o=2.57~\mu\text{F},~L_o/R_o=58.3~\mu\text{H}/\Omega \end{array}$			
For an overview and for information on the interdependencies between the gas group - sensor - nominal diameter, see the "Safety Instructions" (XA) document for the measuring device				

 $1) \qquad \hbox{The gas group depends on the sensor and nominal diameter.}$ 

# Transmitter

Intrinsically safe values

Order code for	Terminal numbers			
"Approval"	Supply voltage		Signal transmission	
	20 (L-)	10 (L+)	62 (A)	72 (B)
<ul> <li>Option BM: ATEX II2G + IECEx Z1 Ex ia, II2D Ex tb</li> <li>Option BO: ATEX II1/2G + IECEx Z0/Z1 Ex ia, II2D</li> <li>Option BQ: ATEX II1/2G + IECEx Z0/Z1 Ex ia</li> <li>Option BU: ATEX II2G + IECEx Z1 Ex ia</li> <li>Option C2: CSA C/US IS Cl. I, II, III Div. 1</li> <li>Option 85: ATEX II2G + IECEx Z1 Ex ia + CSA C/US IS Cl. I, II, III Div. 1</li> </ul>		$I_{i} = 62$ $P_{i} = 2$ $L_{i} =$	6.24 V 23 mA .45 W 0 µH 6 nF	

For an overview and for information on the interdependencies between the gas group - sensor - nominal diameter, see the "Safety Instructions" (XA) document for the measuring device

# Low flow cut off

The switch points for low flow cut off are user-selectable.

# **Galvanic** isolation

The following connections are galvanically isolated from each other:

- Outputs
- Power supply

# Protocol-specific data

# HART

Manufacturer ID	0x11
Device type ID	0x4A
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.
	Measured variables for PV (primary dynamic variable)  Mass flow Volume flow Corrected volume flow Density Reference density Temperature
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable)  Mass flow  Volume flow  Corrected volume flow  Density  Reference density  Temperature  Totalizer 1  Totalizer 2  Totalizer 3
	The range of options increases if the measuring device has one or more application packages.
	Heartbeat Technology Application Package Additional measured variables are available with the Heartbeat Technology application package:  Sensor integrity Carrier pipe temperature Frequency fluctuation 1 Oscillation amplitude 1 Tube damping fluctuation 1 Exciter current 1
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned.  A maximum of 8 device variables can be transmitted:  0 = mass flow  1 = volume flow  2 = corrected volume flow  3 = density  4 = reference density  5 = temperature  6 = totalizer 1  7 = totalizer 2  8 = totalizer 3  9 = dynamic viscosity  10 = kinematic viscosity  11 = temp. compensated dynamic viscosity  12 = temp. compensated kinematic viscosity  13 = target mass flow  14 = carrier mass flow
	<ul> <li>14 = carrier mass flow</li> <li>15 = concentration</li> </ul>

# PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x1561
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under:  ■ www.endress.com  On the product page for the device: Documents/Software → Device drivers  ■ www.profibus.org

Output values (from measuring device to automation system)	Analog input 1 to 8  Mass flow Volume flow Corrected volume flow Target mass flow Density Reference density Concentration Dynamic viscosity Kinematic viscosity Temp. compensated dynamic viscosity Temp. compensated kinematic viscosity Temp. compensated kinematic viscosity Carrier pipe temperature Carrier pipe temperature Electronic temperature Oscillation frequency Oscillation amplitude Frequency fluctuation Oscillation damping Tube damping fluctuation Signal asymmetry Exciter current  Digital input 1 to 2 Partially filled pipe detection Low flow cut off  Totalizer 1 to 3 Mass flow Volume flow Corrected volume flow
Input values (from automation system to measuring device)	Analog output 1 to 3 (fixed assignment)  Pressure Temperature Reference density Digital output 1 to 3 (fixed assignment) Digital output 1: switch positive zero return on/off
	<ul> <li>Digital output 2: perform zero point adjustment</li> <li>Digital output 3: switch switch output on/off</li> <li>Totalizer 1 to 3</li> <li>Totalize</li> <li>Reset and hold</li> <li>Preset and hold</li> <li>Stop</li> <li>Operating mode configuration:         <ul> <li>Net flow total</li> <li>Forward flow total</li> <li>Reverse flow total</li> </ul> </li> </ul>
Supported functions	<ul> <li>Identification &amp; Maintenance         Simplest device identification on the part of the control system and         nameplate</li> <li>PROFIBUS upload/download         Reading and writing parameters is up to ten times faster with PROFIBUS         upload/download</li> <li>Condensed status         Simplest and self-explanatory diagnostic information by categorizing         diagnostic messages that occur</li> </ul>
Configuration of the device address	<ul> <li>DIP switches on the I/O electronics module</li> <li>Via operating tools (e.g. FieldCare)</li> </ul>

# Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1
Device type	Slave
Slave address range	1 to 247

Broadcast address range	0
Function codes	<ul> <li>03: Read holding register</li> <li>04: Read input register</li> <li>06: Write single registers</li> <li>08: Diagnostics</li> <li>16: Write multiple registers</li> <li>23: Read/write multiple registers</li> </ul>
Broadcast messages	Supported by the following function codes:  • 06: Write single registers  • 16: Write multiple registers  • 23: Read/write multiple registers
Supported baud rate	■ 1200 BAUD ■ 2400 BAUD ■ 4800 BAUD ■ 9600 BAUD ■ 19200 BAUD ■ 38400 BAUD ■ 57600 BAUD ■ 115200 BAUD
Data transfer mode	ASCII     RTU
Data access	Each device parameter can be accessed via Modbus RS485.  For Modbus register information

# EtherNet/IP

Protocol	<ul> <li>The CIP Networks Library Volume 1: Common Industrial Protocol</li> <li>The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP</li> </ul>			
Communication type	■ 10Base-T ■ 100Base-TX			
Device profile	Generic device (product type: 0x2B)			
Manufacturer ID	0x49E			
Device type ID	0x104A			
Baud rates	Automatic <sup>10</sup> / <sub>100</sub> Mbit with half-duplex and full-duplex detection			
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs			
Supported CIP connections	Max. 3 connections			
Explicit connections	Max. 6 connections			
I/O connections	Max. 6 connections (scanner)			
Configuration options for measuring device	<ul> <li>DIP switches on the electronics module for IP addressing</li> <li>Manufacturer-specific software (FieldCare)</li> <li>Add-on Profile Level 3 for Rockwell Automation control systems</li> <li>Web browser</li> <li>Electronic Data Sheet (EDS) integrated in the measuring device</li> </ul>			
Configuration of the EtherNet interface	<ul> <li>Speed: 10 MBit, 100 MBit, auto (factory setting)</li> <li>Duplex: half-duplex, full-duplex, auto (factory setting)</li> </ul>			
Configuration of the device address	<ul> <li>DIP switches on the electronics module for IP addressing (last octet)</li> <li>DHCP</li> <li>Manufacturer-specific software (FieldCare)</li> <li>Add-on Profile Level 3 for Rockwell Automation control systems</li> <li>Web browser</li> <li>EtherNet/IP tools, e.g. RSLinx (Rockwell Automation)</li> </ul>			
Device Level Ring (DLR)	No			

RPI	5 ms to 10 s (factory setting: 2	20 ms)	
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0x66	64
	$T \rightarrow O$ configuration:	0x64	44
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	$O \rightarrow T$ configuration:	0x66	64
	$T \rightarrow O$ configuration:	0x64	44
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0xC7	-
	$T \rightarrow O$ configuration:	0x64	44
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	O → T configuration:	0xC7	-
	$T \rightarrow O$ configuration:	0x64	44
	<ul><li>Reference density</li><li>Temperature</li><li>Totalizer 1</li></ul>		
	<ul><li>Totalizer 2</li><li>Totalizer 3</li></ul>		
Configurable Input			
Configurable Input		20 ms)	
RPI	■ Totalizer 3	20 ms)  Instance	Size [byte]
RPI	■ Totalizer 3		Size [byte]
RPI	■ Totalizer 3  5 ms to 10 s (factory setting: 2	Instance	
RPI	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:	Instance 0x68	398
RPI Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:	Instance 0x68 0x66	398 64
RPI Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:	0x68 0x66 0x65	398 64 88
RPI Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:	Instance  0x68  0x66  0x65  Instance	398 64 88
RPI Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:  Instance configuration:	0x68 0x66 0x65 Instance 0x69	398 64 88 Size [byte]
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:  Instance configuration:  O → T configuration:	0x68 0x66 0x65 Instance 0x69 0x66	398 64 88 Size [byte] - 64
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:  Instance configuration:  O → T configuration:	Instance       0x68       0x66       0x65       Instance       0x69       0x66       0x65	398 64 88 Size [byte] - 64 88
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:  O → T configuration:  T → O configuration:	Instance	398 64 88 Size [byte] - 64 88 Size [byte]
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:  O → T configuration:  T → O configuration:  Instance configuration:  T → O configuration:	Instance	398 64 88 Size [byte] - 64 88 Size [byte] 398
Exclusive Owner Multicast  Exclusive Owner Multicast  Input only Multicast	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:  O → T configuration:  T → O configuration:  O → T configuration:  T → O configuration:  O → T configuration:	Instance	398 64 88 Size [byte] - 64 88 Size [byte] 398 -
	■ Totalizer 3  5 ms to 10 s (factory setting: 2  Instance configuration:  O → T configuration:  T → O configuration:  O → T configuration:  T → O configuration:  O → T configuration:  T → O configuration:  O → T configuration:	Instance	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88
Exclusive Owner Multicast  Exclusive Owner Multicast  Input only Multicast	Instance configuration:  O → T configuration:  T → O configuration:	Instance	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88 Size [byte]

Configurable Input Assembly	<ul> <li>Current device diagnostics</li> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>Totalizer 1</li> <li>Totalizer 2</li> <li>Totalizer 3</li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>
Fix Output	
Output Assembly	<ul> <li>Activation of reset totalizers 1-3</li> <li>Activation of pressure compensation</li> <li>Activation of reference density compensation</li> <li>Activation of temperature compensation</li> <li>Reset totalizers 1-3</li> <li>External pressure value</li> <li>Pressure unit</li> <li>External reference density</li> <li>Reference density unit</li> <li>External temperature</li> <li>Temperature unit</li> </ul>
Configuration	
Configuration Assembly	Only the most common configurations are listed below.
	<ul> <li>Software write protection</li> <li>Mass flow unit</li> <li>Volume flow unit</li> <li>Volume unit</li> <li>Corrected volume flow unit</li> <li>Corrected volume unit</li> <li>Density unit</li> <li>Reference density unit</li> <li>Temperature unit</li> <li>Pressure unit</li> <li>Length</li> <li>Totalizer 1-3: <ul> <li>Assignment</li> <li>Unit</li> <li>Measuring mode</li> <li>Failsafe mode</li> </ul> </li> <li>Alarm delay</li> </ul>

# PROFINET

Protocol	"Application layer protocol for decentral device periphery and distributed automation", version 2.3
Conformity class	В
Communication type	100 MBit/s
Device profile	Application interface identifier 0xF600 Generic device
Manufacturer ID	0x11
Device type ID	0x844A
Device description files (GSD, DTM)	Information and files under:  ■ www.endress.com  On the product page for the device: Documents/Software → Device drivers  ■ www.profibus.org
Baud rates	Automatic 100 Mbit/s with full-duplex detection

Cycle times	From 8 ms
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Supported connections	<ul> <li>1 x AR (Application Relation)</li> <li>1 x Input CR (Communication Relation)</li> <li>1 x Output CR (Communication Relation)</li> <li>1 x Alarm CR (Communication Relation)</li> </ul>
Configuration options for measuring device	<ul> <li>DIP switches on the electronics module, for device name assignment (last part)</li> <li>Manufacturer-specific software (FieldCare, DeviceCare)</li> <li>Web browser</li> <li>Device master file (GSD), can be read out via the integrated Web server of the measuring device</li> </ul>
Configuration of the device name	<ul> <li>DIP switches on the electronics module, for device name assignment (last part)</li> <li>DCP protocol</li> </ul>
Output values (from measuring device to automation system)	Analog Input module (slot 1 to 14)  Mass flow  Volume flow  Corrected volume flow  Target mass flow  Carrier mass flow  Density  Reference density  Concentration  Dynamic viscosity  Temp. compensated dynamic viscosity  Temp. compensated kinematic viscosity  Temp. compensated kinematic viscosity  Carrier pipe temperature  Carrier pipe temperature  Carrier pipe temperature  Coscillation frequency  Oscillation amplitude  Frequency fluctuation  Oscillation damping  Tube damping fluctuation  Signal asymmetry  Exciter current  Discrete Input module (slot 1 to 14)  Empty pipe detection  Low flow cut off  Diagnostics Input module (slot 1 to 14)  Last diagnostics  Current diagnosis  Totalizer 1 to 3 (slot 15 to 17)  Mass flow  Volume flow  Corrected volume flow  Heartbeat Verification module (fixed assignment)
	Verification status (slot 23)  The range of options increases if the measuring device has one or more application packages.

Input values (from automation system to measuring device)	Analog Output module (fixed assignment)  External pressure (slot 18)  External temperature (slot 19)  External reference density (slot 20)  Discrete Output module (fixed assignment)  Activate/deactivate positive zero return (slot 21)  Perform zero point adjustment (slot 22)
	Totalizer 1 to 3 (slot 15 to 17)  Totalize  Reset and hold  Preset and hold  Stop  Operating mode configuration:  Net flow total  Forward flow total  Reverse flow total
	Heartbeat Verification module (fixed assignment) Start verification (slot 23)  The range of options increases if the measuring device has one or more application packages.
Supported functions	<ul> <li>Identification &amp; Maintenance         Simple device identification via:         <ul> <li>Control system</li> <li>Nameplate</li> </ul> </li> <li>Measured value status         <ul> <li>The process variables are communicated with a measured value status</li> </ul> </li> <li>Blinking feature via the onsite display for simple device identification and assignment</li> </ul>

# Administration of software options

Input/output value	Process variable	Category	Slot
Output value	Mass flow	Process variable	114
	Volume flow		
	Corrected volume flow		
	Density		
	Reference density		
	Temperature		
	Electronic temperature		
	Oscillation frequency		
	Frequency fluctuation		
	Oscillation damping		
	Oscillation frequency		
	Signal asymmetry		
	Exciter current		
	Empty pipe detection		
	Low flow cut off		
	Current device diagnostics		
	Previous device diagnostics		
Output value	Target mass flow	Concentration 1)	114
	Carrier mass flow		
	Concentration		
Output value	Dynamic viscosity	Viscosity 2)	114

Input/output value	Process variable	Category	Slot	
	Kinematic viscosity			
	Temp. compensated dynamic viscosity			
	Temp. compensated kinematic viscosity			
Output value	Carrier pipe temperature	Heartbeat 3)	114	
	Oscillation damping 1			
	Oscillation frequency 1			
	Oscillation amplitude 0			
	Oscillation amplitude 1			
	Frequency fluctuation 1			
	Tube damping fluctuation 1			
	Exciter current 1			
	Sensor integrity			
Input value	External density	Process monitoring	18	
	External temperature		19	
	External reference density		20	
	Flow override		21	
	Zero point adjustment		22	
	Verification status	Heartbeat Verification	23	

- Only available with the "Concentration" application package. Only available with the "Viscosity" application package. Only available with the "Heartbeat" application package.
- 1) 2) 3)

# Startup configuration

# Startup configuration (NSU)

If startup configuration is enabled, the configuration of the most important device parameters is taken from the automation system and used.


The following configuration is taken from the automation system:

- Management
  - Software revision
  - Write protection
- System units
  - Mass flow
  - Mass
  - Volume flow
  - Volume
  - Corrected volume flow
  - Corrected volume
  - Density
  - Reference density
  - Temperature
  - Pressure
- Viscosity application package
  - Dynamic viscosity
  - Kinematic viscosity
- Concentration application package
  - Coefficients A0 to A4
  - Coefficients B1 to B3
- Sensor adjustment
- Process param.
  - Damping (flow, density, temperature)
  - Flow override
- Low flow cut off
  - Assign process variable
  - Switch-on/switch-off point
  - Pressure shock suppression
- Empty pipe detection
  - Assign process variable
  - Limit values
  - Response time
  - Max. damping
- Corrected volume flow calculation
  - External reference density
  - Fixed reference density
  - Reference temperature
  - Linear expansion coefficient
- Square expansion coefficient
- Measuring mode
  - Medium
  - Gas type
  - Reference sound velocity
  - Temperature coefficient sound velocity
- External compensation
  - Pressure compensation
  - Pressure value
  - External pressure
- Diagnostic settings
- Diagnostic settings
   Diagnostic behavior for diverse diagnostic information

# Power supply

# Terminal assignment

# Overview: housing version and connection versions



A0016770

- Housing version: compact, aluminum coated
- Housing version: compact, hygienic, stainless В
- С Housing version: ultra-compact, hygienic, stainless
- Connection version: 4-20 mA HART, pulse/frequency/switch output 1
- 1.1 Signal transmission: pulse/frequency/switch output1.2 Signal transmission: 4-20 mA HART
- 1.3 Supply voltage
- Connection version: Modbus RS485
- 2.1 Signal transmission
- 2.2 Supply voltage
- Connection versions: EtherNet/IP and PROFINET 3
- 3.1 Signal transmission
- 3.2 Supply voltage
- Connection version: PROFIBUS DP
- 4.1 Signal transmission
- 4.2 Supply voltage

# Transmitter

Connection version 4-20 mA HART with pulse/frequency/switch output


Order code for "Output", option  ${\bf B}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Possible options for order code
"Housing"	Outputs	Power supply	"Electrical connection"
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G ½"</li> <li>Option D: thread NPT ½"</li> </ul>
Options A, B	Device plugs → 🖺 31	Terminals	■ Option L: plug M12x1 + thread NPT ½" ■ Option N: plug M12x1 + coupling M20 ■ Option P: plug M12x1 + thread G ½" ■ Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🖺 31	Device plugs → 🖺 31	Option <b>Q</b> : 2 x plug M12x1

Order code for "Housing":

- Option A: compact, coated aluminum
- Option **B**: compact, hygienic, stainless
- lacktriangle Option lacktriangle ultra-compact, hygienic, stainless



A00168

- 2 Terminal assignment 4-20 mA HART with pulse/frequency/switch output
- 1 Power supply: DC 24 V
- 2 Output 1: 4-20 mA HART (active)
- 3 Output 2: pulse/frequency/switch output (passive)

	Terminal number					
Order code for "Output"	Power supply		Output 1		Output 2	
2	2 (L-)	1 (L+)	27 (-)	26 (+)	25 (-)	24 (+)
Option <b>B</b>	DC 24 V		4-20 mA HART (active)		Pulse/frequency/switch output (passive)	

Order code for "Output":

Option B: 4-20 mA HART with pulse/frequency/switch output

# PROFIBUS DP connection version

For use in the non-hazardous area and Zone 2/Div. 2.


Order code for "Output", option  ${\bf L}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Describle entions for order sode
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G ½"</li> <li>Option D: thread NPT ½"</li> </ul>
Options A, B	Device plugs → 🖺 31	Terminals	■ Option L: plug M12x1 + thread NPT ½" ■ Option N: plug M12x1 + coupling M20 ■ Option P: plug M12x1 + thread G ½" ■ Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🖺 31	Device plugs → 🖺 31	Option <b>Q</b> : 2 x plug M12x1

Order code for "Housing":

- Option **A**: compact, coated aluminum
- Option B: compact, hygienic, stainless
   Option C ultra-compact, hygienic, stainless



- ₩ 3 PROFIBUS DP terminal assignment
- Power supply: DC 24 V
- PROFIBUS DP

	Terminal number			
Order code for	Power supply		Output	
"Output"	2 (L-)	1 (L+)	26 (RxD/TxD-P)	27 (RxD/TxD- N)
Option <b>L</b>	DC 24 V		В	А

Order code for "Output":

Option L: PROFIBUS DP, for use in non-hazardous areas and Zone 2/div. 2

26

Modbus RS485 connection version

For use in the non-hazardous area and Zone 2/Div. 2.


Order code for "Output", option  $\boldsymbol{M}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for "Housing"	Connection me	thods available	Possible options for order code
	Output	Power supply	"Electrical connection"
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G ½"</li> <li>Option D: thread NPT ½"</li> </ul>
Options A, B	Device plugs → 🖺 31	Terminals	■ Option L: plug M12x1 + thread NPT ½" ■ Option N: plug M12x1 + coupling M20 ■ Option P: plug M12x1 + thread G ½" ■ Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🖺 31	Device plugs → 🖺 31	Option <b>Q</b> : 2 x plug M12x1

Order code for "Housing":

- $\, \bullet \,$  Option A: compact, coated aluminum
- Option B: compact, hygienic, stainless
   Option C ultra-compact, hygienic, stainless



- € 4 Modbus RS485 terminal assignment, connection version for use in non-hazardous areas and Zone 2/Div.
- Power supply: DC 24 V
- Modbus RS485

	Terminal number				
Order code for "Output"	Power supply		Output		
<b>-</b>	2 (L-)	1 (L+)	27 (B)	26 (A)	
Option <b>M</b>	DC 24 V		Modbus	RS485	

Order code for "Output":

Option M Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2

Modbus RS485 connection version

i

For use in the intrinsically safe area. Connection via Safety Barrier Promass 100.


Order code for "Output", option  ${\bf M}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Describle entions for order sode
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G ½"</li> <li>Option D: thread NPT ½"</li> </ul>
A, B, C	Device plugs → 🖺 31		Option I: plug M12x1

Order code for "Housing":

- Option **A**: compact, coated aluminum
- Option **B**: compact, hygienic, stainless
- Option **C** ultra-compact, hygienic, stainless



A0017053

- Modbus RS485 terminal assignment, connection version for use in intrinsically safe areas (connection via Safety Barrier Promass 100)
- 1 Intrinsically safe power supply
- 2 Modbus RS485

Order code for "Output"	20 (L-)	10 (L+)	72 (B)	62 (A)
Option <b>M</b>	Intrinsically saf	e supply voltage	Modbus RS485	intrinsically safe

Order code for "Output":

Option  $\mathbf{M}$ : Modbus RS485, for use in intrinsically safe areas (connection via Safety Barrier Promass 100)

EtherNet/IP connection version


Order code for "Output", option  ${\bf N}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Descible entions for order sode	
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"	
Options A, B	Device plugs → 🖺 31	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>	
Options A, B, C	Device plugs → 🖺 31	Device plugs → 🖺 31	Option <b>Q</b> : 2 x plug M12x1	

Order code for "Housing":

- Option **A**: compact, coated aluminum
- Option B: compact, hygienic, stainless
   Option C ultra-compact, hygienic, stainless



- **№** 6 EtherNet/IP terminal assignment
- Power supply: DC 24 V
- EtherNet/IP

	Terminal number				
Order code for "Output"	Power	supply	Output		
	2 (L-)	1 (L+)	Device plug M12x1		
Option N	DC 24 V		EtherNet/IP		
Order code for "Output": Option <b>N</b> : EtherNet/IP					

# PROFINET connection version


Order code for "Output", option  ${\bf R}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Descible entires for order and	
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"	
Options A, B	Device plugs → 🖺 31	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>	
Options A, B, C	Device plugs → 🖺 31	Device plugs → 🖺 31	Option <b>Q</b> : 2 x plug M12x1	

Order code for "Housing":


- Option **A**: compact, coated aluminum
- Option B: compact, hygienic, stainless
   Option C ultra-compact, hygienic, stainless



- **₽** 7 PROFINET terminal assignment
- Power supply: DC 24 V
- PROFINET

	Terminal number				
Order code for "Output"	Power	supply	Output		
4.0	2 (L-)	1 (L+)	Device plug M12x1		
Option R	DC 24 V		PROFINET		
Order code for "Output": Option <b>R</b> : PROFINET					

# **Safety Barrier Promass 100**



- Safety Barrier Promass 100 with terminals
- 1 Non-hazardous area and Zone 2/Div. 2
- 2 Intrinsically safe area


# Pin assignment, device plug

- Order codes for the M12x1 connectors, see the "Order code for **electrical connection**" column:
  - 4-20 mA HART, pulse/frequency/switch output → 🖺 25
  - PROFIBUS DP→ 🖺 26
  - Modbus RS485 → 🗎 27
  - EtherNet/IP → 🖺 29
  - PROFINET→ 🗎 30

# Supply voltage

For all connection versions except MODBUS RS485 intrinsically safe (device side)

P Device plug MODBUS RS485 intrinsically safe with supply voltage → 🖺 32



- The f
- The following is recommended as a socket:
  - Binder, series 763, part no. 79 3440 35 05
  - Alternatively: Phoenix part no. 1669767 SAC-5P-M12MS
    - With the order code for "Output", option **B**: 4-20 mA HART, pulse/frequency/switch output
    - With the order code for "Output", option N: EtherNet/IP
  - When using the device in a hazardous location: Use a suitably certified socket.

# 4-20 mA HART with pulse/frequency/switch output

Device plug for signal transmission (device side)


2	Pin		Assignment
550	1	+	4-20 mA HART (active)
1 1 0 0 0 3	2	-	4-20 mA HART (active)
	3	+	Pulse/frequency/switch output (passive)
5	4	-	Pulse/frequency/switch output (passive)
4 A0016810	5		Grounding/shielding
	Cod	ling	Plug/socket
	A	A	Socket

- Recommended plug: Binder, series 763, part no. 79 3439 12 05
  - When using the device in a hazardous location, use a suitably certified plug.

### **PROFIBUS DP**

For use in the non-hazardous area and Zone 2/Div. 2.


Device plug for signal transmission (device side)



- Recommended plug: Binder, series 763, part no. 79 4449 20 05
  When using the device in a hazardous location, use a suitably certified plug.

# **MODBUS RS485**


Device plug for signal transmission with supply voltage (device side), MODBUS RS485 (intrinsically safe)



- Recommended socket: Binder, series 763, part no. 79 3439 12 05
  When using the device in a hazardous location: Use a suitably certified socket.

Device plug for signal transmission (device side), MODBUS RS485 (not intrinsically safe)

For use in the non-hazardous area and Zone 2/Div. 2.



- Recommended plug: Binder, series 763, part no. 79 4449 20 05
- When using the device in a hazardous location, use a suitably certified plug.

# EtherNet/IP

Device plug for signal transmission (device side)

2	Pin		Assignment
	1	+	Tx
1 3	2	+	Rx
	3	1	Tx
	4	-	Rx
4	Cod	ling	Plug/socket
	I	)	Socket

Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q
- When using the device in a hazardous location, use a suitably certified plug.

# **PROFINET**

Device plug for signal transmission (device side)

2	Pin		Assignment
	1	+	TD+
$1 \longrightarrow 3$	2	+	RD +
	3	-	TD -
	4	-	RD -
4 A0016812	Cod	ling	Plug/socket
	I	)	Socket



Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q
- When using the device in a hazardous location, use a suitably certified plug.

Supply voltage

The power unit must be tested to ensure it meets safety requirements (e.g. PELV, SELV).

# Transmitter

For device version with communication type:

- HART, PROFIBUS DP, EtherNet/IP: DC 20 to 30 V
- Modbus RS485, device version:
  - For use in the non-hazardous area and Zone 2/Div. 2: DC 20 to 30 V
  - For use in the intrinsically safe area: power supply via Safety Barrier Promass 100

# **Safety Barrier Promass 100**

DC 20 to 30 V

# Power consumption

# Transmitter

Order code for "Output"	Maximum Power consumption
Option <b>B</b> : 4-20 mA HART with pulse/frequency/switch output	3.5 W
Option L: PROFIBUS DP	3.5 W
Option <b>M</b> Modbus RS485, for use in non-hazardous areas and Zone 2/ Div. 2	3.5 W
Option <b>M</b> : Modbus RS485, for use in intrinsically safe areas	2.45 W
Option N: EtherNet/IP	3.5 W
Option R: PROFINET	3.5 W

# Safety Barrier Promass 100

Order code for "Output"	Maximum Power consumption
Option <b>M</b> : Modbus RS485, for use in intrinsically safe areas	4.8 W

# **Current consumption**

# Transmitter

Order code for "Output"	Maximum Current consumption	Maximum switch-on current
Option <b>B</b> : 4-20mA HART, pul./freq./switch output	145 mA	18 A (< 0.125 ms)
Option <b>L</b> : PROFIBUS DP	145 mA	18 A (< 0.125 ms)
Option <b>M</b> Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2	90 mA	10 A (< 0.8 ms)
Option <b>M</b> : Modbus RS485, for use in intrinsically safe areas	145 mA	16 A (< 0.4 ms)
Option <b>N</b> : EtherNet/IP	145 mA	18 A (< 0.125 ms)
Option R: PROFINET	145 mA	18 A (< 0.125 ms)

# Safety Barrier Promass 100


Order code for "Output"	Maximum Current consumption	Maximum switch-on current
Option $\mathbf{M}$ : Modbus RS485, for use in intrinsically safe areas	230 mA	10 A (< 0.8 ms)

# Power supply failure

- Totalizers stop at the last value measured.
- Depending on the device version, the configuration is retained in the device memory or in the plug-in memory (HistoROM DAT).
- Configuration is retained in the plug-in memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

# **Electrical connection**

# Connecting the transmitter




- Housing version: compact, aluminum coated Α
- В Housing version: compact hygienic, stainless
- Cable entry or device plug for signal transmission
- 2 Cable entry or device plug for supply voltage
- С Housing version: ultra-compact, hygienic, stainless, M12 device plug
- Device plug for signal transmission
- Device plug for supply voltage

- In the case of device versions with a connector, the transmitter housing does not need to be opened to connect the signal cable or power supply cable.


# Connection examples

Current output 4-20 mA HART



- ₽9 Connection example for 4-20 mA HART current output (active)
- Automation system with current input (e.g. PLC)
- 2 Cable shield, observe cable specifications
- 3 Connection for HART operating devices
- Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load
- Analog display unit: observe maximum load
- Transmitter


# Pulse/frequency output



 $\blacksquare 10$  Connection example for pulse/frequency output (passive)

- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply


# Switch output



A001680

- $\blacksquare$  11 Connection example for switch output (passive)
- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply3 Transmitter: o
- 3 Transmitter: observe input values


#### PROFIBUS DP



- $\blacksquare$  12 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2
- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Transmitter
- If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

Modbus RS485


Modbus RS485, non-hazardous area and Zone 2/Div. 2



 $\blacksquare$  13 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter


## Modbus RS485 intrinsically safe



Connection example for Modbus RS485 intrinsically safe

- 1
- Control system (e.g. PLC) Cable shield, observe cable specifications
- 3 Safety Barrier Promass 100
- 4 Observe cable specifications
- Non-hazardous area 5
- 6 Non-hazardous area and Zone 2/Div. 2
- Intrinsically safe area
- 8 Transmitter


#### EtherNet/IP



**■** 15 Connection example for EtherNet/IP

- 1 Control system (e.g. PLC)
- Ethernet switch 2
- 3 Observe cable specifications
- Device plug 4
- Transmitter


## PROFINET



**■** 16 Connecting cable for PROFINET

- 1 Control system (e.g. PLC)
- 2 3 Ethernet switch
- Observe cable specifications
- Connector
- Transmitter


## HART input



A0019828

**■** 17 Connection example for HART input (burst mode) via current output (active)

- Cable shield, observe cable specifications
- Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load
- 2 3 Connection for HART operating devices
- 4 Analog display unit
- Transmitter
- Sensor for external measured variable



■ 18 Connection example for HART input (master mode) via current output (active)

- 1 Automation system with current input (e.g. PLC).
  Prerequisite: automation system with HART version 6, HART commands 113 and 114 can be processed.
- 2 Cable shield, observe cable specifications
- 3 Resistor for HART communication (≥ 250  $\Omega$ ): observe maximum load
- 4 Connection for HART operating devices
- 5 Analog display unit
- 6 Transmitter
- 7 Sensor for external measured variable

#### Potential equalization

#### Requirements

No special measures for potential equalization are required.

Please consider the following to ensure correct measurement:

- Same electrical potential for the fluid and sensor
- Company-internal grounding concepts



For devices intended for use in hazardous locations, please observe the guidelines in the  ${\sf Ex}$  documentation (XA).

#### Terminals

#### Transmitter

Spring terminals for wire cross-sections 0.5 to 2.5 mm<sup>2</sup> (20 to 14 AWG)

## **Safety Barrier Promass 100**

Plug-in screw terminals for wire cross-sections 0.5 to 2.5 mm<sup>2</sup> (20 to 14 AWG)

#### Cable entries

- Cable gland: M20 × 1.5 with cable  $\phi$ 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
  - NPT ½"
  - G ½"
  - M20

#### Cable specification

#### Permitted temperature range

- $-40 ^{\circ}\text{C} (-40 ^{\circ}\text{F}) \text{ to } +80 ^{\circ}\text{C} (+176 ^{\circ}\text{F})$
- Minimum requirement: cable temperature range ≥ ambient temperature +20 K

#### Power supply cable

Standard installation cable is sufficient.

#### Signal cable

Current output

For 4-20 mA HART: Shielded cable recommended. Observe grounding concept of the plant.

Pulse/frequency/switch output

Standard installation cable is sufficient.

#### PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A			
Characteristic impedance	35 to 165 $\Omega$ at a measuring frequency of 3 to 20 MHz			
Cable capacitance	30 pF/m			
Wire cross-section	0.34 mm <sup>2</sup> (22 AWG)			
Cable type	Twisted pairs			
Loop resistance	≤110 Ω/km			
Signal damping	Max. 9 dB over the entire length of the cable cross-section			
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.			

#### Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A		
Characteristic impedance	135 to 165 $\Omega$ at a measuring frequency of 3 to 20 MHz		
Cable capacitance	30 pF/m		
Wire cross-section	>0.34 mm <sup>2</sup> (22 AWG)		
Cable type	Twisted pairs		
Loop resistance	≤110 Ω/km		
Signal damping	Max. 9 dB over the entire length of the cable cross-section		
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.		

## EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.



For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization

## PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.



For more information on planning and installing PROFINET networks, see: "PROFINET Cabling and Interconnection Technology", Guideline for PROFINET

## Connecting cable between Safety Barrier Promass 100 and measuring device $\,$

Cable type	Shielded twisted-pair cable with 2x2 wires. When grounding the cable shield, observe the grounding concept of the plant.
Maximum cable resistance	$2.5 \Omega$ , one side

Comply with the maximum cable resistance specifications to ensure the operational reliability of the measuring device.


The maximum cable length for individual wire cross-sections is specified in the table below. Observe the maximum capacitance and inductance per unit length of the cable and connection values for hazardous areas .

Wire cross-section		Maximum cable length	
[mm <sup>2</sup> ]	[AWG]	[m]	[ft]
0.5	20	70	230
0.75	18	100	328
1.0	17	100	328
1.5	16	200	656
2.5	14	300	984

## Performance characteristics

# Reference operating conditions

- Error limits based on ISO 11631
- Water with +15 to +45 °C (+59 to +113 °F) at 2 to 6 bar (29 to 87 psi)
- Specifications as per calibration protocol
- Accuracy based on accredited calibration rigs that are traced to ISO 17025.



#### Maximum measured error

o.r. = of reading;  $1 \text{ g/cm}^3 = 1 \text{ kg/l}$ ; T = medium temperature

## Base accuracy



Design fundamentals → 🖺 45

Mass flow and volume flow (liquids)

±0.10 % o.r.

Mass flow (gases)

±0.50 % o.r.

Density (liquids)

	Under reference operating conditions		Standard density calibration 1)		range ification <sup>2) 3)</sup>
[g/cm³]	[lbs/in³]	[g/cm³]	[lbs/in³]	[g/cm³]	[lbs/in³]
±0.0005	±0.00097	±0.02	±0.039	±0.004	±0.0078

- 1) Valid over the entire temperature and density range
- Valid range for special density calibration: 0 to 2 g/cm³, +5 to +80  $^{\circ}$ C (+41 to +176  $^{\circ}$ F)
- Order code for "Application package", option EF "Special density and concentration " or EH "Special density and viscosity"

## Temperature

 $\pm 0.5 \,^{\circ}\text{C} \pm 0.005 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.9 \,^{\circ}\text{F} \pm 0.003 \cdot (\text{T} - 32) \,^{\circ}\text{F})$ 

42

## Zero point stability

DN		Zero point stability	
[mm]	[in]	[kg/h]	[lb/min]
8	3/8	0.150	0.0055
15	1/2	0.488	0.0179
15 FB	½ FB	1.350	0.0496
25	1	1.350	0.0496
25 FB	1 FB	3.375	0.124
40	11/2	3.375	0.124
40 FB	1 ½ FB	5.25	0.193
50	2	5.25	0.193
50 FB	2 FB	13.5	0.496
80	3	13.5	0.496
FB = Full bore		,	

## Flow values

Flow values as turndown parameter depending on nominal diameter.

## SI units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[mm]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]
8	2 000	200	100	40	20	4
15	6500	650	325	130	65	13
15 FB	18 000	1800	900	360	180	36
25	18 000	1800	900	360	180	36
25 FB	45 000	4500	2 250	900	450	90
40	45 000	4500	2 250	900	450	90
40 FB	70 000	7 000	3 500	1400	700	140
50	70 000	7 000	3 500	1400	700	140
50 FB	180 000	18 000	9 000	3 600	1800	360
80	180 000	18 000	9 000	3 600	1800	360
FB = Full bore						

## US units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[inch]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]
3/8	73.50	7.350	3.675	1.470	0.735	0.147
1/2	238.9	23.89	11.95	4.778	2.389	0.478
½ FB	661.5	66.15	33.08	13.23	6.615	1.323
1	661.5	66.15	33.08	13.23	6.615	1.323
1 FB	1654	165.4	82.70	33.08	16.54	3.308
1½	1654	165.4	82.70	33.08	16.54	3.308
1½ FB	2 573	257.3	128.7	51.46	25.73	5.146

DN	1:1	1:10	1:20	1:50	1:100	1:500
[inch]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]
2	2 573	257.3	128.7	51.46	25.73	5.146
2 FB	6 6 1 5	661.5	330.8	132.3	66.15	13.23
3	6 6 1 5	661.5	330.8	132.3	66.15	13.23
FB = Full bo	FB = Full bore					

### Accuracy of outputs



In the case of analog outputs, the output accuracy must also be considered for the measured error; in contrast, this need not be considered in the case of fieldbus outputs (e.g. Modbus RS485, EtherNet/IP).

The outputs have the following base accuracy specifications.

Current output

Accuracy	Max. ±5 μA
----------	------------

Pulse/frequency output

o.r. = of reading

Accuracy Max. ±5	O ppm o.r. (across the entire ambient temperature range)
------------------	--

## Repeatability

o.r. = of reading;  $1 \text{ g/cm}^3 = 1 \text{ kg/l}$ ; T = medium temperature

## Base repeatability

Mass flow and volume flow (liquids)

±0.05 % o.r.

Mass flow (gases)

±0.25 % o.r.



Design fundamentals  $\rightarrow \triangle 45$ 

## Density (liquids)

 $\pm 0.00025 \text{ g/cm}^3$ 

## Temperature

 $\pm 0.25 \,^{\circ}\text{C} \pm 0.0025 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.45 \,^{\circ}\text{F} \pm 0.0015 \cdot (\text{T}-32) \,^{\circ}\text{F})$ 

## Response time

The response time depends on the configuration (damping).

## Influence of ambient temperature

### **Current output**

o.r. = of reading

Temperature coefficient	Max. ±0.005% o.r./°C
-------------------------	----------------------

## Pulse/frequency output

Temperature coefficient	No additional effect. Included in accuracy.
-------------------------	---

## Influence of medium temperature

## Mass flow and volume flow


When there is a difference between the temperature for zero point adjustment and the process temperature, the typical measured error of the sensor is  $\pm 0.0002$  % of the full scale value/°C  $(\pm 0.0001 \% \text{ of the full scale value/°F}).$ 

### Density

When there is a difference between the density calibration temperature and the process temperature, the typical measured error of the sensor is  $\pm 0.0001$  g/cm³ /°C ( $\pm 0.00005$  g/cm³ /°F). Field density calibration is possible.

## Wide-range density specification (special density calibration)

If the process temperature is outside the valid range ( $\rightarrow \triangleq 42$ ) the measured error is  $\pm 0.0001 \text{ g/cm}^3 \text{ °C } (\pm 0.00005 \text{ g/cm}^3 \text{ °F})$ 



A0016614

- Field density calibration, for example at +20  $^{\circ}$ C (+68  $^{\circ}$ F)
- 2 Special density calibration

#### **Temperature**

 $\pm 0.005 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.005 \cdot (\text{T} - 32) \,^{\circ}\text{F})$ 

# Influence of medium pressure

The table below shows the effect on accuracy of mass flow due to a difference between calibration pressure and process pressure.

o.r. = of reading

DN		[% o.r./bar]	[% o.r./psi]	
[mm]	[in]			
8	3/8	No effect	No effect	
15	1/2	No effect	No effect	
15 FB	½ FB	+0.003	+0.0002	
25	1	+0.003	+0.0002	
25 FB	1 FB	No effect	No effect	
40	11/2	No effect	No effect	
40 FB	1½ FB	No effect	No effect	
50	2	No effect	No effect	
50 FB	2 FB	No effect	No effect	
80	3	No effect	No effect	
FB = Full bore				

## Design fundamentals

o.r. = of reading, o.f.s. = of full scale value

BaseAccu = base accuracy in % o.r., BaseRepeat = base repeatability in % o.r.

MeasValue = measured value; ZeroPoint = zero point stability


Calculation of the maximum measured error as a function of the flow rate

Flow rate	Maximum measured error in % o.r.
$\geq \frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$	± BaseAccu
A002133	
< ZeroPoint BaseAccu · 100	± ZeroPoint MeasValue · 100
A002133	A0021334

 ${\it Calculation of the maximum repeatability as a function of the flow rate}$ 

Flow rate	Maximum repeatability in % o.r.
$\geq \frac{\frac{1}{2} \cdot \text{ZeroPoint}}{\text{BaseRepeat}} \cdot 100$	± BaseRepeat
A0021335	
$<\frac{\frac{1}{2} \cdot ZeroPoint}{BaseRepeat} \cdot 100$	$\pm \frac{1}{2} \cdot \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$
A0021336	A0021337

## Example for max. measured error




- E Error: Maximum measured error as % o.r. (example)
- Q Flow rate as %

## Installation

No special measures such as supports are necessary. External forces are absorbed by the construction of the device.

## Mounting location




To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

## Installation in down pipes

However, the following installation suggestion allows for installation in an open vertical pipeline. Pipe restrictions or the use of an orifice with a smaller cross-section than the nominal diameter prevent the sensor running empty while measurement is in progress.



A0015596

- 19 Installation in a down pipe (e.g. for batching applications)
- 1 Supply tank
- 2 Sensor
- 3 Orifice plate, pipe restriction
- 4 Valve
- 5 Batching tank

D	N	Ø orifice plate,	pipe restriction
[mm]	[in]	[mm]	[in]
8	3/8	6	0.24
15	1/2	10	0.40
15 FB	½ FB	15	0.60
25	1	14	0.55
25 FB	1 FB	24	0.95
40	1½	22	0.87
40 FB	1½ FB	35	1.38
50	2	28	1.10
50 FB	2 FB	54	2.13
80	3	50	1.97
FB = Full bore			

## Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

	Orientatio	Recommendation	
A	Vertical orientation	A0015591	₩ ₩
В	Horizontal orientation, transmitter head up	A0015589	Exceptions:

	Recommendation		
С	Horizontal orientation, transmitter head down	A0015590	Exceptions:
D	Horizontal orientation, transmitter head at side	A0015592	

- 1) Applications with low process temperatures may decrease the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.
- Applications with high process temperatures may increase the ambient temperature. To maintain the 2) maximum ambient temperature for the transmitter, this orientation is recommended.


#### Inlet and outlet runs

No special precautions need to be taken for fittings which create turbulence, such as valves, elbows or T-pieces, as long as no cavitation occurs  $\rightarrow \implies 57$ .

### Special mounting instructions

## Complete drainability guaranteed

When the sensor is installed in a horizontal line, eccentric clamps can be used to ensure complete drainability. When the system is pitched in a specific direction and at a specific slope, gravity can be used to achieve complete drainability. The sensor must be mounted in the correct position to ensure full drainability in the horizontal position. Markings on the sensor show the correct mounting position to optimize drainability.




- Eccentric clamp connection
- "This side up" label indicates which side is up 2
- 3 Slope the device in accordance with the hygiene guidelines. Slope: approx. 2 % or 21 mm/m (0.24 in/feet)
- Line on the underside indicates the lowest point of the eccentric process connection.

## Securing with mounting clamp in the case of hygiene connections

It is not necessary to provide additional support for the sensor for operational performance purposes. If, however, additional support is required for installation purposes, the following dimensions must be observed.

Use mounting clamp with lining between clamp and measuring instrument.




DN		A		В		С	
[mm]	[in]	[mm]	[in]	[mm]	[in]	[mm]	[in]
8	8	373	14.69	20	0.79	40	1.57
15	15	409	16.1	20	0.79	40	1.57
15 FB	15 FB	539	21.22	30	1.18	44.5	1.75
25	25	539	21.22	30	1.18	44.5	1.75
25 FB	25 FB	668	26.3	28	1.1	60	2.36
40	40	668	26.3	28	1.1	60	2.36
40 FB	40 FB	780	30.71	35	1.38	80	3.15
50	50	780	30.71	35	1.38	80	3.15
50 FB	50 FB	1 152	45.35	57	2.24	90	3.54
80	80	1 152	45.35	57	2.24	90	3.54

## Zero point adjustment

Experience shows that zero point adjustment is advisable only in special cases:

- To achieve maximum measuring accuracy even with low flow rates
- Under extreme process or operating conditions (e.g. very high process temperatures or very high-viscosity fluids).

# Mounting Safety Barrier Promass 100



A0016894

20 Minimum distance between additional Safety Barrier Promass 100 or other modules. Engineering unit mm (in)

## **Environment**

## Ambient temperature range

Measuring device	Non-Ex	-40 to +60 °C (-40 to +140 °F)
Ex na, NI version		-40 to +60 °C (-40 to +140 °F)
		<ul> <li>−40 to +60 °C (−40 to +140 °F)</li> <li>−50 to +60 °C (−58 to +140 °F) (order code for "Test, certificate", option JM))</li> </ul>

Readability of the local display	-20 to $+60$ °C ( $-4$ to $+140$ °F) The readability of the display may be impaired at temperatures outside the temperature range.
Safety Barrier Promass 100	-40 to +60 °C (-40 to +140 °F)

► If operating outdoors:

Avoid direct sunlight, particularly in warm climatic regions.

Weather protection covers can be ordered from Endress+Hauser: see "Accessories" section

## Temperature tables

In the following tables, the following interdependencies between the maximum medium temperature  $T_{\rm m}$  for T6 to T1 and the maximum ambient temperature  $T_{\rm a}$  apply when operating the device in hazardous areas.

## Ex ia, cCSA<sub>US</sub> IS

## SI units

Order code for "Housing"	T <sub>a</sub> [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]
Option A "Compact coated alu"	35	50	85	120	150	150	150
Option B "Compact hygienic,	50	-	85	120	150	150	150
stainless"	60	_	-	120	150	150	150
	35	50	85	120	150	150	150
Option C "Ultra-compact, hygienic, stainless"	45	-	85	120	150	150	150
	50	ı	-	120	150	150	150

#### US units

Order code for "Housing"	T <sub>a</sub> [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]
Option A "Compact coated alu"	95	122	185	248	302	302	302
Option B "Compact hygienic,	122	_	185	248	302	302	302
stainless"	140	-	-	248	302	302	302
	95	122	185	248	302	302	302
Option C "Ultra-compact, hygienic, stainless"	113	-	185	248	302	302	302
	122	-	-	248	302	302	302

## Ex nA, $_{\text{C}}\text{CSA}_{\text{US}}$ NI

## SI units

Order code for "Housing"	T <sub>a</sub> [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300°C]	T1 [450 °C]
Option A "Compact coated alu"	35	50	85	120	150	150	150
Option B "Compact hygienic,	50	-	85	120	150	150	150
stainless"	60	-	-	120	150	150	150
Option C "Ultra-compact, hygienic,	50	-	85	120	150	150	150
stainless"	60	-	-	120	150	150	150

#### US units

Order code for "Housing"	T <sub>a</sub> [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]
Option A "Compact coated alu"	95	122	185	248	302	302	302
Option B "Compact hygienic,	122	-	185	248	302	302	302
stainless"	140	-	-	248	302	302	302
Option C "Ultra-compact, hygienic,	122	-	185	248	302	302	302
stainless"	140	-	-	248	302	302	302

Explosion hazards arising from gas and dust

## Determining the temperature class and surface temperature with the temperature table

- ullet In the case of gas: Determine the temperature class as a function of the ambient temperature  $T_a$  and the medium temperature  $T_m$ .
- In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature T<sub>a</sub> and the maximum medium temperature T<sub>m</sub>.

#### Example

- Measured maximum ambient temperature:  $T_{ma}$  = 47 °C ■ Measured maximum medium temperature:  $T_{mm}$  = 108 °C
- 4. [°C] [85°C] [100°C] 135°C 1200°C [300°C] [450°C] 35 50 85 120 140 140 140 50 85 140 140 60 120 140 140 140 35 85 140 140 140 45 85 120 140 140 140 50 120

A0019758

 $\blacksquare$  21 Procedure for determining the maximum surface temperature

1.

- 1. Select device (optional).
- 2. In the column for the maximum ambient temperature  $T_a$  select the temperature that is immediately greater than or equal to the measured maximum ambient temperature  $T_{ma}$  that is present.

3.

 $T_a = 50 \,^{\circ}\text{C}$ .

The row showing the maximum medium temperature is determined.

2.

- 3. Select the maximum medium temperature  $T_m$  of this row, which is larger or equal to the measured maximum medium temperature  $T_{mm}$ .
  - The column with the temperature class for gas is determined:  $108 \,^{\circ}\text{C} \le 120 \,^{\circ}\text{C} \rightarrow T4$ .
- 4. The maximum temperature of the temperature class determined corresponds to the maximum surface temperature for dust:  $T4 = 135 \,^{\circ}C$

#### Storage temperature

- -40 to +80 °C (-40 to +176 °F), preferably at +20 °C (+68 °F) (standard version)
- -50 to +80 °C (-58 to +176 °F) (Order code for "Test, certificate", option JM)

#### Climate class

DIN EN 60068-2-38 (test Z/AD)

#### Degree of protection

#### Transmitter and sensor

- As standard: IP66/67, type 4X enclosure
- With the order code for "Sensor options", option **CM**: IP69K can also be ordered
- When housing is open: IP20, type 1 enclosure
- Display module: IP20, type 1 enclosure

### **Safety Barrier Promass 100**

IP20

#### Vibration resistance

#### Compact version

- Vibration, sinusoidal according to IEC 60068-2-6
  - 2 to 8.4 Hz, 3.5 mm peak
  - 8.4 to 2000 Hz, 1 g peak
- Vibration broad-band random, according to IEC 60068-2-64
  - 10 to 200 Hz, 0.003 g<sup>2</sup>/Hz
  - 200 to 2000 Hz, 0.001 g<sup>2</sup>/Hz
  - Total: 1.54 g rms

#### Shock resistance

## Compact version

Shock, half-sine according to IEC 60068-2-27 6 ms 30 g

#### Shock resistance

## **Compact version**

Rough handling shocks according to IEC 60068-2-31

## Interior cleaning

- Cleaning in place (CIP)
- Sterilization in place (SIP)
- Cleaning with pigs

#### **Options**

Oil- and grease-free version for wetted parts, without inspection certificate Order code for "Service", option **HA** 

# Electromagnetic compatibility (EMC)

- Depends on the communication protocol:
  - HART, PROFIBUS DP, Modbus RS485, EtherNet/IP:
     As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)
  - PROFINET: as per IEC/EN 61326
- Complies with emission limits for industry as per EN 55011 (Class A)
- Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170
   Volume 2, IEC 61784



The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.




For details, refer to the Declaration of Conformity.

## **Process**

Medium temperature range

 $-50 \text{ to } +150 \,^{\circ}\text{C} \, (-58 \text{ to } +302 \,^{\circ}\text{F})$ 

## Dependency of ambient temperature on medium temperature



Exemplary representation, values in the table below.

- Ambient temperature range
- $T_m$  Medium temperature
- Maximum permitted medium temperature  $T_m$  at  $T_{a max}$  = 60 °C (140 °F); higher medium temperatures  $T_m$ require a reduced ambient temperature  $T_a$
- Maximum permitted ambient temperature  $T_a$  for the maximum specified medium temperature  $T_m$  of the
- Values for devices used in the hazardous area: Separate Ex documentation (XA) for the device .


Density

0 to  $5000 \text{ kg/m}^3$  (0 to 312 lb/cf)

## Pressure-temperature ratings


The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.

## Flange according to EN 1092-1 (DIN 2501)




With flange material 1.4301 (304); wetted parts: titanium **■** 23

## Flange according to ASME B16.5




 $\blacksquare$  24 With flange material 1.4301 (304); wetted parts: titanium

## Flange JIS B2220




 $\blacksquare$  25 With flange material 1.4301 (304). Wetted parts: titanium.

## Flange DIN 11864-2 Form A



■ 26 With flange material Grade 2 titanium


#### Thread DIN 11851



**2**7 With connection material Grade 2 titanium


DIN 11851 allows for applications up to +140  $^{\circ}$ C (+284  $^{\circ}$ F) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

#### Thread DIN 11864-1 Form A



With connection material Grade 2 titanium ₹ 28

## Thread ISO 2853




₹ 29 With connection material Grade 2 titanium

55 Endress+Hauser

A0029888-EN

#### Thread SMS 1145



■ 30 With connection material Grade 2 titanium

SMS 1145 allows for applications up to 16 bar (232 psi) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

#### Tri-Clamp

The clamp connections are suitable up to a maximum pressure of 16 bar (232 psi). Please observe the operating limits of the clamp and seal used as they can be over 16 bar (232 psi). The clamp and seal are not included in the scope of supply.

#### Sensor housing

The sensor housing is filled with dry nitrogen gas and protects the electronics and mechanics inside.

If a measuring tube fails (e.g. due to process characteristics like corrosive or abrasive fluids), the fluid will initially be contained by the sensor housing.

If the sensor is to be purged with gas (gas detection), it should be equipped with purge connections.

Do not open the purge connections unless the containment can be filled immediately with a dry, inert gas. Use only low pressure to purge.

Maximum pressure: 5 bar (72.5 psi)

#### Burst pressure of the sensor housing

The following sensor housing burst pressures are only valid for standard devices and/or devices equipped with closed purge connections (not opened/as delivered).

If a device fitted with purge connections (order code for "Sensor option", option CH "Purge connection") is connected to the purge system, the maximum pressure is determined by the purge system itself or by the device, depending on which component has the lower pressure classification.

The sensor housing burst pressure refers to a typical internal pressure which is reached prior to mechanical failure of the sensor housing and which was determined during type testing. The corresponding type test declaration can be ordered with the device (order code for "Additional approval", option LN "Sensor housing burst pressure, type test").

D	N	Sensor housing burst pressure				
[mm]	[in]	[bar]	[psi]			
8	3/8	220	3 190			
15	1/2	220	3 190			
15 FB	½ FB	235	3 408			
25	1	235	3 408			
25 FB	1 FB	220	3 190			
40	1½	220	3 190			
40 FB	1 ½ FB	235	3 408			
50	2	235	3 408			

D	N	Sensor housing burst pressure			
[mm]	[in]	[bar]	[psi]		
50 FB	2 FB	460	6670		
80	3	460	6670		
FB = Full bore					


For information on the dimensions: see the "Mechanical construction" section

#### Flow limit

Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.

- For an overview of the full scale values for the measuring range, see the "Measuring range" section  $\rightarrow \stackrel{ riangle}{=} 8$
- The minimum recommended full scale value is approx. 1/20 of the maximum full scale value
- In most applications, 20 to 50 % of the maximum full scale value can be considered ideal
- A low full scale value must be selected for abrasive media (such as liquids with entrained solids): flow velocity < 1 m/s (< 3 ft/s).
- For gas measurement the following rules apply:
  - The flow velocity in the measuring tubes should not exceed half the sound velocity (0.5 Mach).
  - The maximum mass flow depends on the density of the gas: formula  $\rightarrow \triangleq 8$
- To calculate the flow limit, use the *Applicator* sizing tool  $\rightarrow \stackrel{\triangle}{=} 92$

#### Pressure loss




#### System pressure

It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas. This is prevented by means of a sufficiently high system pressure.

For this reason, the following mounting locations are recommended:

- At the lowest point in a vertical pipe
- Downstream from pumps (no danger of vacuum)



A0028777

## Thermal insulation

In the case of some fluids, it is important to keep the heat radiated from the sensor to the transmitter to a low level. A wide range of materials can be used for the required insulation.


The following device versions are recommended for versions with thermal insulation: Version with extended neck for insulation:

Order code for "Sensor option", option CG with an extended neck length of 105 mm (4.13 in).

### NOTICE

## Electronics overheating on account of thermal insulation!

- ▶ Recommended orientation: horizontal orientation, transmitter housing pointing downwards.
- ▶ Do not insulate the transmitter housing .
- ► Maximum permissible temperature at the lower end of the transmitter housing: 80 °C (176 °F)
- ► Thermal insulation with extended neck free: We recommend that you do not insulate the extended neck in order to ensure optimum dissipation of heat.



■ 31 Thermal insulation with extended neck free

#### Heating

Some fluids require suitable measures to avoid loss of heat at the sensor.

### **Heating options**

- Electrical heating, e.g. with electric band heaters
- Via pipes carrying hot water or steam
- Via heating jackets
  - Heating jackets for the sensors can be ordered as accessories from Endress+Hauser.

## NOTICE

#### Danger of overheating when heating

- ► Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F).
- ▶ Ensure that sufficient convection takes place at the transmitter neck.
- ► Ensure that a sufficiently large area of the transmitter neck remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.
- ▶ When using in potentially explosive atmospheres, observe the information in the device-specific Ex documentation. For detailed information on the temperature tables, see the separate document entitled "Safety Instructions" (XA) for the device.

#### **Vibrations**

The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by plant vibrations.


58

## Mechanical construction

## Dimensions in SI units

## **Compact version**

Order code for "Housing", option A "Compact coated aluminum"



A0016456


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E 1) 2) [mm]	F <sup>1) 2)</sup> [mm]	G [mm]	L [mm]
8	136	147.5	93.5	54	207.2	264.4	8.55	3)
15	136	147.5	93.5	54	207.2	264.4	11.38	3)
15 FB	136	147.5	93.5	54	207.2	264.4	17.07	3)
25	136	147.5	93.5	54	216.9	274.1	17.07	3)
25 FB	136	147.5	93.5	54	216.9	287.6	26.40	3)
40	136	147.5	93.5	54	231.2	301.9	26.40	3)
40 FB	136	147.5	93.5	54	231.2	315.4	35.62	3)
50	136	147.5	93.5	54	256.6	340.8	35.62	3)
50 FB	136	147.5	93.5	54	256.6	366.2	54.8	3)
80	136	147.5	93.5	54	256.6	366.2	54.8	3)
FB = Full bore								

<sup>1)</sup> If using an extension neck for the extended temperature range, order code for "Sensor option", option CG: values +70 mm

<sup>2)</sup> If using a display, order code for "Display; Operation", option B: values +28 mm

<sup>3)</sup> Depends on the particular process connection

## Order code for "Housing", option B "Compact hygienic, stainless"




A0016522

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E <sup>2)</sup> [mm]	F <sup>1) 2)</sup> [mm]	G [mm]	L [mm]
8	133.5	136.8	78	58.8	202.2	264.4	8.55	3)
15	133.5	136.8	78	58.8	202.2	264.4	11.38	3)
15 FB	133.5	136.8	78	58.8	202.2	264.4	17.07	3)
25	133.5	136.8	78	58.8	211.9	274.1	17.07	3)
25 FB	133.5	136.8	78	58.8	211.9	287.6	26.40	3)
40	133.5	136.8	78	58.8	226.2	301.9	26.40	3)
40 FB	133.5	136.8	78	58.8	226.2	315.4	35.62	3)
50	133.5	136.8	78	58.8	251.6	340.8	35.62	3)
50 FB	133.5	136.8	78	58.8	251.6	366.2	54.8	3)
80	133.5	136.8	78	58.8	251.6	366.2	54.8	3)
FB = Full bore								

- 1) If using an extension neck for the extended temperature range, order code for "Sensor option", option CG: values  $\pm 70~\text{mm}$
- 2) If using a display, order code for "Display; Operation", option B: values +14 mm
- 3) Depends on the particular process connection

## Order code for "Housing", option C "Ultra-compact hygienic, stainless"




DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E <sup>2)</sup> [mm]	F <sup>1)2)</sup> [mm]	G [mm]	L [mm]
8	111.4	123.6	67.7	55.9	202.2	264.4	8.56	3)
15	111.4	123.6	67.7	55.9	202.2	264.4	11.38	3)
15 FB	111.4	123.6	67.7	55.9	202.2	264.4	17.07	3)
25	111.4	123.6	67.7	55.9	211.9	274.1	17.07	3)
25 FB	111.4	123.6	67.7	55.9	211.9	287.6	26.37	3)
40	111.4	123.6	67.7	55.9	226.2	301.9	26.37	3)
40 FB	111.4	123.6	67.7	55.9	226.2	315.4	35.62	3)
50	111.4	123.6	67.7	55.9	251.6	340.8	35.62	3)
50 FB	111.4	123.6	67.7	55.9	251.6	366.2	54.76	3)
80	111.4	123.6	67.7	55.9	251.6	366.2	54.76	3)
FB = Full bo	FB = Full bore							

- 1) If using an extension neck for the extended temperature range, order code for "Sensor option", option CG: values +70 mm
- 2) If using a display, order code for "Display; Operation", option B: values +14 mm
- 3) Depends on the particular process connection

## Flange connections

Fixed flange EN 1092-1, ASME B16.5, JIS B2220



Length tolerance for dimension L in mm: +1.5 / -2.0

1.4301 (304),	Flange according to EN 1092-1 (DIN 2501) Form B1 (DIN 2526 Form C): PN 40 1.4301 (304), wetted parts: titanium Order code for "Process connection", option D2W							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]		
8 1)	95	65	4 × Ø14	16	17.30	403		
15	95	65	4 × Ø14	16	17.30	439		
15 FB	95	65	4 × Ø14	15	17.07	573		
25	115	85	4 × Ø14	19	28.50	579		
25 FB	115	85	4 × Ø14	18	25.60	702		
40	150	110	4 × Ø18	22	43.10	707.5		
40 FB	150	110	4 × Ø18	20	35.62	821		
50	165	125	4 × Ø18	24	54.50	829		

# Flange according to EN 1092-1 (DIN 2501) Form B1 (DIN 2526 Form C): PN 40 1.4301 (304), wetted parts: titanium

Order code for "Process connection", option D2W

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
50 FB	165	125	4 × Ø18	36	54.8	1211.5
80	200	160	8 × Ø18	33	82.5	1211

FB = Full bore

Surface roughness: Ra 3.2 to 12.5  $\mu m$ 

## 1) DN 8 with DN 15 flanges as standard

# Flange according to EN 1092-1 (DIN 2501) Form B2 (DIN 2526 Form E): PN 63 1.4301 (304), wetted parts: titanium

Order code for "Process connection", option D3W

		•				
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
50	180	135	4 × Ø22	34	54.5	833
50 FB	180	135	4 × Ø22	45	54.8	1211.5
80	215	170	8 × Ø22	41	81.7	1211

FB = Full bore

Surface roughness (flange): Ra 0.8 to 3.2  $\mu m$ 

# Flange according to EN 1092-1 (DIN 2501) Form B2 (DIN 2526 Form E): PN 100 1.4301 (304), wetted parts: titanium

Order code for "Process connection", option D4W

Oraci coae joi	Order code for Trocess connection, option D4W							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]		
8 1)	105	75	4 × Ø14	25	17.30	403		
15	105	75	4 × Ø14	25	17.30	439		
15 FB	105	75	4 × Ø14	26	17.07	573		
25	140	100	4 × Ø18	29	28.50	579		
25 FB	140	100	4 × Ø18	31	25.60	702		
40	170	125	4 × Ø22	32	42.50	707.5		
40 FB	170	125	4 × Ø22	33	35.62	821		
50	195	145	4 × Ø26	36	53.90	833		
50 FB	195	145	4 × Ø26	48	54.8	1211.5		
80	230	180	8 × Ø26	58	80.9	1236.5		
1								

FB = Full bore

Surface roughness (flange): Ra 0.8 to 3.2  $\mu m$ 

## 1) DN 8 with DN 15 flanges as standard

#### Flange according to ASME B16.5: Class 150 1.4301 (304), wetted parts: titanium Order code for "Process connection", option AAW В С D Е DN L Α [mm] [mm] [mm] [mm] [mm] [mm] [mm] 8 1) 90 60.3 $4 \times Ø15.7$ 20 15.70 403 15.70 15 90 60.3 4 × Ø15.7 20 439

Flange according to ASME B16.5: Class 150
1.4301 (304), wetted parts: titanium
Order code for "Process connection" ontion A AIM

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
15 FB	90	60.3	4 × Ø15.7	19	17.07	573
25	110	79.4	4 × Ø15.7	23	26.70	579
25 FB	110	79.4	4 × Ø15.7	22	25.60	702
40	125	98.4	4 × Ø15.7	26	40.90	707.5
40 FB	125	98.4	4 × Ø15.7	24	35.62	821
50	150	120.7	4 × Ø19.1	28	52.60	829
50 FB	150	120.7	4 × Ø19.1	40	54.8	1211.5
80	190	152.4	4 × Ø19.1	37	78	1211

FB = Full bore

Surface roughness (flange): Ra 3.2 to 6.3 µm

#### 1) DN 8 with DN 15 flanges as standard

#### 

168.3

20 15.70 403 15 95 66.7  $4 \times Ø15.7$ 20 15.70 439 4 × Ø15.7 15 FB 95 66.7 19 17.07 573 25 88.9 4 × Ø19.1 23 579 125 26.70 25 FB 125 88.9 4 × Ø19.1 25.60 702 22 40 155 114.3  $4 \times \emptyset 22.4$ 26 40.90 707.5 40 FB 155 114.3  $4 \times \emptyset 22.4$ 24 35.62 821 50 127.0  $8 \times Ø19.1$ 52.60 829 165 28 50 FB 127.0 165  $8 \times Ø19.1$ 43 54.8 1211.5

 $8 \times \emptyset 22.3$ 

D

[mm]

42

Ε

[mm]

L

[mm]

1211

80 FB = Full bore

Surface roughness (flange): Ra 3.2 to  $6.3~\mu m$ 

210

#### 1) DN 8 with DN 15 flanges as standard

#### Flange according to ASME B16.5: Class 600 1.4301 (304), wetted parts: titanium Order code for "Process connection", option ACW DN В С D Ε Α L [mm] [mm] [mm] [mm] [mm] [mm] [mm] 8 1) 95 66.7 $4 \times Ø15.7$ 20 13.80 403 95 66.7 4 × Ø15.7 20 13.80 439 15 15 FB 95 66.7 4 × Ø15.7 22 17.07 573 579 25 125 88.9 $4 \times Ø19.1$ 23 24.40 25 FB 125 88.9 $4 \times \emptyset 19.1$ 25 25.60 702 155 114.3 $4 \times \emptyset 22.4$ 38.10 707.5 40 28

# Flange according to ASME B16.5: Class 600 1.4301 (304), wetted parts: titanium

Order code for "Process connection", option **ACW** 

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
40 FB	155	114.3	4 × Ø22.4	29	35.62	821
50	165	127.0	8 × Ø19.1	33	49.30	833
50 FB	165	127.0	8 × Ø19.1	46	54.8	1211.5
80	210	168.3	8 × Ø22.3	53	73.7	1223

FB = Full bore

Surface roughness (flange): Ra 3.2 to 6.3  $\mu m$ 

#### 1) DN 8 with DN 15 flanges as standard

#### Flange JIS B2220: 10K 1.4301 (304), wetted parts: titanium Order code for "Process connection", option NDW С D Е Α [mm] [mm] [mm] [mm] [mm] [mm] [mm] 50 155 120 $4 \times Ø19$ 28 50 829 50 FB 195 145 1211.5 $4\times \emptyset 26$ 48 54.8

 $8 \times \emptyset 18$ 

37

82.5

1211

80 FB = Full bore

Surface roughness (flange): Ra 3.2 to 6.3  $\mu m$ 

200

160

Flange JIS B2220: 20K 1.4301 (304), wetted parts: titanium Order code for "Process connection", option NEW							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]	
8 1)	95	70	4 × Ø15	20	15.00	403	
15	95	70	4 × Ø15	20	15.00	439	
15 FB	95	70	4 × Ø15	19	17.07	573	
25	125	90	4 × Ø19	23	25.00	579	
25 FB	125	90	4 × Ø19	22	25.60	702	
40	140	105	4 × Ø19	26	40.00	707.5	
40 FB	140	105	4 × Ø19	24	35.62	821	
50	155	120	8 × Ø19	28	50.00	829	
50 FB	155	120	8 × Ø19	42	54.8	1211.5	
80	200	160	8 × Ø23	36	80	1211	
FB = Full bore	noss (flango): P	a 2 2 to 6 2					

Surface roughness (flange): Ra 3.2 to 6.3 μm

1) DN 8 with DN 15 flanges as standard

Flange JIS B2220: 40K 1.4301 (304), wetted parts: titanium Order code for "Process connection", option NFW							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]	
8 1)	115	80	4 × Ø19	25	15.00	403	
15	115	80	4 × Ø19	25	15.00	439	
15 FB	115	80	4 × Ø19	26	17.07	573	
25	130	95	4 × Ø19	27	25.00	579	
25 FB	130	95	4 × Ø19	29	25.60	702	
40	160	120	4 × Ø23	30	38.00	707.5	
40 FB	160	120	4 × Ø23	31	35.62	821	

8 × Ø19

 $8 \times \emptyset 19$ 

 $8 \times \emptyset 23$ 

32

43

46

50.00

54.8

75

829

1211.5

1211

80 FB = Full bore

50

50 FB

Surface roughness (flange): Ra 3.2 to 6.3  $\mu m$ 

165

165

210

130

130


170

## 1) DN 8 with DN 15 flanges as standard

Flange JIS B2220: 63K 1.4301 (304), wetted parts: titanium Order code for "Process connection", option NHW							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]	
8 1)	120	85	4 × Ø19	28	12.00	403	
15	120	85	4 × Ø19	28	12.80	439	
15 FB	120	85	4 × Ø19	29	17.07	573	
25	140	100	4 × Ø23	30	22.00	579	
25 FB	140	100	4 × Ø23	32	25.60	702	
40	175	130	4 × Ø25	36	35.00	707.5	
40 FB	175	130	4 × Ø25	37	35.62	821	
50	185	145	8 × Ø23	40	48.00	833	
50 FB	185	145	8 × Ø23	47	54.8	1211.5	
80	230	185	8 × Ø25	55	73	1226.5	

1) DN 8 with DN 15 flanges as standard

## Fixed flange DIN 11864-2



Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. **■** 32

Length tolerance for dimension L in mm: +1.5 / -2.0


Flange DIN11864-2 Form A, for pipe according to DIN11866 series A, flange with notch  Titanium  Order code for "Process connection", option KFW							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]	
8 1)	54	37	4 × Ø9	10	10	448	
15	59	42	4 × Ø9	10	16	484	
25	70	53	4 × Ø9	10	26	622	
40	82	65	4 × Ø9	10	38	750	
50	94	77	4 × Ø9	10	50	872	
80	133	112	8 × Ø11	12	81	1269	

3A version available: order code for "Additional approval", option LP in conjunction with  $Ra_{max}$  = 0.76  $\mu m$ : order code for "Measuring tube material", option CB or  $Ra_{max}$  = 0.38  $\mu m$ : order code for "Measuring tube material", option CD

1) DN 8 with DN 10 flanges

## **Clamp connections**

## Tri-Clamp



Length tolerance for dimension L in mm: +1.5 / -2.0

Tri-Clamp ( ≥ 1"), DIN 11866 series C  Titanium  Order code for "Process connection", option FTW							
DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]			
8	1	50.4	22.1	426			
15	1	50.4	22.1	462			
15 FB	see ¾" Tri-Clamp com	see ¾" Tri-Clamp connection					
25	1	50.4	22.1	602			
25 FB	1	50.4	22.1	730.5			
40	1 ½	50.4	34.8	730.5			
40 FB	1 ½	50.4	34.8	850			
50	2	63.9	47.5	850			
50 FB <sup>1)</sup>	2 ½	77.4	60.3	1268.5			
80	3	90.9	72.9	1268.5			

FB = Full bore

3A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max}$  = 0.76  $\mu$ m: order code for "Measuring tube material", option CB or

 $Ra_{max} = 0.38 \ \mu m$ : order code for "Measuring tube material", option CD

## 1) Order code for "Process connection", option FRW

3/4" Tri-Clamp, DIN 11866 series C Titanium Order code for "Process connection", option FEW							
DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]			
8	3/4	25.0	16.0	426			
15	3/4	25.0	16.0	462			
15 FB	3/4	25.0	16.0	602			

FB = Full bore

3A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max}$  = 0.76  $\mu m$  : order code for "Measuring tube material", option CB or

 $Ra_{max}$  = 0.38  $\mu m$ : order code for "Measuring tube material", option CD

#### ½" Tri-Clamp, DIN 11866 series C Titanium Order code for "Process connection", option FBW DN Clamp В [mm] [in] [mm] [mm] [mm] 8 25.0 9.5 426 15 25.0 9.5 462

3A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max}$  = 0.76 µm: order code for "Measuring tube material", option CB or  $Ra_{max}$  = 0.38 µm: order code for "Measuring tube material", option CD


Eccentric Tri-Cl	Eccentric Tri-Clamp, DIN 11866 series C Titanium							
DN [mm]	Order Code for "Process connection", Option	Clamp [in]	A [mm]	B [mm]	L [mm]			
8	FEA	1/2	25	9.5	426			
15	FEC	3/4	25	15.75	462			
15 FB	FEE	1	50.5	22.1	602			
25	FEE	1	50.5	22.1	602			
25 FB	FEG	1½	50.5	34.8	730.5			
40	FEG	1½	50.5	34.8	730.5			
40 FB	FEJ	2	64	47.5	850			
50	FEJ	2	64	47.5	850			
50 FB	FEL	2 ½	77.5	60.3	1268.5			
50 FB	FEM	3	91	72.9	1268.5			
80	FEL	2 ½	77.5	60.3	1268.5			
80	FEM	3	91	72.9	1268.5			

3A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max}=0.76~\mu m$ : order code for "Measuring tube material", option CB or  $Ra_{max}=0.38~\mu m$ : order code for "Measuring tube material", option CD Additional information on "Eccentric clamps"

## Couplings

#### Thread DIN 11851



A0015628

Length tolerance for dimension L in mm: +1.5 / -2.0

#### Thread DIN 11851, for pipe according to DIN11866, series A Titanium Order code for "Process connection", option KCW DN В L [mm] [in] [mm] [mm] 8 Rd $34 \times 1/8$ 16 426 15 Rd $34 \times 1/8$ 16 462 15 FB 602 Rd $34 \times 1/8$ 16 25 Rd 52 × 1/6 26 602 25 FB Rd $52 \times 1/6$ 26 737 40 Rd 65 × 1/6 38 730.5 40 FB Rd $65 \times 1/6$ 38 856 50 Rd 78 × 1/6 50 856 1268.5 50 FB Rd $78 \times 1/6$ 50 Rd 110 × 1/4 81 1268.5

FB = Full bore

3A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max} = 0.76 \mu m$ : order code for "Measuring tube material", option CB

Thread Rd 28 × 1/8" DIN 11851, for pipe according to DIN11866 series A  Titanium  Order code for "Process connection", option KAW						
DN [mm]	A [in]	B [mm]	L [mm]			
8	Rd 28 × 1/8	10	426			
15	Rd 28 × 1/8	10	462			

3A version available: order code for "Additional approval", option LP in conjunction with  $Ra_{max}$  = 0.76  $\mu m$ : order code for "Measuring tube material", option CB

Thread DIN11864-1 Form A, for pipe according to DIN11866, series A Titanium Order code for "Process connection", option KEW							
A [in]	B [mm]	L [mm]					
Rd 28 × 1/8	10	426					
Rd 34 × 1/8	16	462					
Rd 34 × 1/8	16	602					
Rd 52 × 1/6	26	602					
Rd 52 × 1/6	26	735					
Rd 65 × 1/6	38	730.5					
Rd 65 × 1/6	38	856					
Rd 78 × 1/6	50	856					
Rd 78 × 1/6	50	1268.5					
Rd 110 × 1/4	81	1268.5					
	A [in]  Rd 28 × 1/8  Rd 34 × 1/8  Rd 34 × 1/8  Rd 52 × 1/6  Rd 52 × 1/6  Rd 65 × 1/6  Rd 65 × 1/6  Rd 78 × 1/6  Rd 78 × 1/6	A [in] B [mm]  Rd 28 × 1/8 10  Rd 34 × 1/8 16  Rd 34 × 1/8 16  Rd 52 × 1/6 26  Rd 52 × 1/6 26  Rd 65 × 1/6 38  Rd 65 × 1/6 38  Rd 78 × 1/6 50  Rd 78 × 1/6 50					


FB = Full bore

3A version available (order code for "Additional approval", option LP) in combination with Ra $_{max}$  = 0.76  $\mu$ m, Ra $_{max}$  = 0.38  $\mu$ m (order code for "Measuring tube material", option CB, CD)

1) DN 8 with DN 10 thread as standard

Thread SMS 1145 Titanium Order code for "Process connection", option SAW							
DN [mm]	A [in]	B [mm]	L [mm]				
8	Rd 40 × 1/6	22.5	426				
15	Rd 40 × 1/6	22.5	462				
25	Rd 40 × 1/6	22.5	602				
25 FB	Rd 40 × 1/6	22.5	737				
40	Rd 60 × 1/6	35.5	738.5				
40 FB	Rd 60 × 1/6	35.5	858				
50	Rd 70 × 1/6	48.5	858				
50 FB	Rd 70 × 1/6	48.5	1258.5				
80 Rd 98 × 1/6 72 1268.5							
FB = Full bore 3A version available (Ra <sub>r</sub>	FB = Full bore 3A version available ( $Ra_{max} = 0.76 \mu m$ ) (order code for "Additional approval", option LP)						

## Thread ISO 2853



A001562

Length tolerance for dimension L in mm: +1.5 / -2.0

Thread ISO 2853, for pipe according to ISO 2037 Titanium Order code for "Process connection", option JSE					
DN [mm]	A [in]	B [mm]	L [mm]		
8 <sup>1)</sup>	37.13	22.6	434		
15	37.13	22.6	470		
15 FB	37.13	22.6	610		
25 FB	37.13	22.6	745		
40	50.65	35.6	736.5		
40 FB	50.65	35.6	861		
50	64.16	48.6	858		
50 FB	64.1	48.6	1268.5		

# Thread ISO 2853, for pipe according to ISO 2037 Titanium

Order code for "Process connection", option JSE

DN [mm]			L [mm]	
80	91.19	72.9	1268.5	

FB = Full bore


3A version available (order code for "Additional approval", option LP) in combination with  $Ra_{max}$  = 0.76  $\mu$ m,  $Ra_{max}$  = 0.38  $\mu$ m (order code for "Measuring tube material", option CB, CD)

1) DN 8 with DN 15 thread as standard

## **Safety Barrier Promass 100**

Top-hat rail EN 60715:

- TH 35 x 7.5
- TH 35 x 15




A001677

A	В	С	D
[mm]	[mm]	[mm]	[mm]
108	114.5	99	22.5

#### Accessories

Purge connections / secondary containment monitoring

Order code for "Sensor options", option CH



A000332


DN	G	Н	L	
[mm]	[in]	[mm]	[mm]	
8	½-NPT	90.65	122	
15	½-NPT	90.65	158	

DN	G	Н	L	
[mm]	[in]	[mm]	[mm]	
15 FB	½-NPT	90.65	158	
25	½-NPT	90.65	296	
25 FB	½-NPT	90.65	296	
40	½-NPT	103.35	392	
40 FB	½-NPT	103.35	392	
50	½-NPT	117.75	488	
50 FB	½-NPT	145.5	814	
80	½-NPT	145.5	814	

## **Dimensions in US units**

## Compact version


Order code for "Housing", option A "Compact coated aluminum"



DN [in]	A [in]	B [in]	C [in]	D [in]	E <sup>2)</sup> [in]	F <sup>1) 2)</sup> [in]	G [in]	L [in]
3/8	5.35	5.81	3.68	2.13	8.16	10.41	0.34	3)
1/2	5.35	5.81	3.68	2.13	8.16	10.41	0.45	3)
½ FB	5.35	5.81	3.68	2.13	8.16	10.41	0.67	3)
1	5.35	5.81	3.68	2.13	8.54	10.79	0.67	3)
1 FB	5.35	5.81	3.68	2.13	8.54	11.32	1.01	3)
11/2	5.35	5.81	3.68	2.13	9.1	11.89	1.01	3)
1½ FB	5.35	5.81	3.68	2.13	9.1	12.42	1.40	3)
2	5.35	5.81	3.68	2.13	10.1	13.42	1.40	3)
2 FB	5.35	5.81	3.68	2.13	10.1	14.42	2.16	3)
3	5.35	5.81	3.68	2.13	10.1	14.42	2.16	3)
FB = Full bore								

- 1) If using an extension neck for the extended temperature range, order code for "Sensor option", option CG: values +2.76 in
- If using a display, order code for "Display; Operation", option B: values +1.1 in Depends on the particular process connection
- 2) 3)

#### Order code for "Housing", option B "Compact hygienic, stainless"




A0016522

DN [in]	A [in]	B [in]	C [in]	D [in]	E <sup>2)</sup> [in]	F <sup>1) 2)</sup> [in]	G [in]	L [in]
3/8	5.26	5.39	3.07	2.31	7.96	10.41	0.34	3)
1/2	5.26	5.39	3.07	2.31	7.96	10.41	0.45	3)
½ FB	5.26	5.39	3.07	2.31	7.96	10.41	0.67	3)
1	5.26	5.39	3.07	2.31	8.34	10.79	0.67	3)
1 FB	5.26	5.39	3.07	2.31	8.34	11.32	1.01	3)
11/2	5.26	5.39	3.07	2.31	8.91	11.89	1.01	3)
1½ FB	5.26	5.39	3.07	2.31	8.91	12.42	1.40	3)
2	5.26	5.39	3.07	2.31	9.91	13.42	1.40	3)
2 FB	5.26	5.39	3.07	2.31	9.91	14.42	2.16	3)
3	5.26	5.39	3.07	2.31	9.91	14.42	2.16	3)
FB = Full bo	ore	•					*	

- 1) If using an extension neck for the extended temperature range, order code for "Sensor option", option CG: values  $\pm 2.76$  in
- 2) If using a display, order code for "Display; Operation", option B: values +0.55 in
- 3) Depends on the particular process connection

#### Order code for "Housing", option C "Ultra-compact hygienic, stainless"




A0016521

DN [in]	A [in]	B [in]	C [in]	D [in]	E <sup>2)</sup> [in]	F <sup>1) 2)</sup> [in]	G [in]	L [in]
3/8	4.39	4.87	2.67	2.2	7.96	10.41	0.337	3)
1/2	4.39	4.87	2.67	2.2	7.96	10.41	0.448	3)
½ FB	4.39	4.87	2.67	2.2	7.96	10.41	0.672	3)
1	4.39	4.87	2.67	2.2	8.34	10.79	0.672	3)
1 FB	4.39	4.87	2.67	2.2	8.34	11.32	1.038	3)
1½	4.39	4.87	2.67	2.2	8.91	11.89	1.038	3)
1½ FB	4.39	4.87	2.67	2.2	8.91	12.42	1.402	3)
2	4.39	4.87	2.67	2.2	9.91	13.42	1.402	3)
2 FB	4.39	4.87	2.67	2.2	9.91	14.42	2.156	3)
3	4.39	4.87	2.67	2.2	9.91	14.42	2.156	3)
FB = Full bo	ore							

- 1) If using an extension neck for the extended temperature range, order code for "Sensor option", option CG: values +2.76 in
- 2) 3) If using a display, order code for "Display; Operation", option B: values  $\pm 0.55$  in
- Depends on the particular process connection

#### Flange connections

Fixed flange ASME B16.5



Length tolerance for dimension L in inch:  $\pm 0.06\ /\ -0.08$ 

Flange according to ASME B16.5: Class 150 1.4301 (304), wetted parts: titanium Order code for "Process connection", option AAW							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]	
3/8 1)	3.54	2.37	4 × Ø0.62	0.79	0.62	15.87	
1/2	3.54	2.37	4 × Ø0.62	0.79	0.62	17.28	
½ FB	3.54	2.37	4 × Ø0.62	0.75	0.67	22.56	
1	4.33	3.13	4 × Ø0.62	0.91	1.05	22.8	
1 FB	4.33	3.13	4 × Ø0.62	0.87	1.01	27.64	
1½	4.92	3.87	4 × Ø0.62	1.02	1.61	27.85	
1½ FB	4.92	3.87	4 × Ø0.62	0.94	1.4	32.32	
2	5.91	4.75	4 × Ø0.75	1.1	2.07	32.64	

Flange according to ASME B16.5: Class 150 1.4301 (304), wetted parts: titanium Order code for "Process connection", option AAW						
DN         A         B         C         D         E         L           [in]         [in]         [in]         [in]         [in]						
2 FB	5.91	4.75	4 × Ø0.75	1.57	2.16	47.7
3	7.48	6.00	4 × Ø0.75	1.46	3.07	47.68
FB = Full bore Surface roughne	ss (flange): Ra	126 to 248 µ	iin			

1) DN 3/8" with DN ½" flanges as standard;

Flange according to ASME B16.5: Class 300 L.4301 (304), wetted parts: titanium Order code for "Process connection", option ABW									
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]			
3/8 1)	3.74	2.63	4 × Ø0.62	0.79	0.62	15.87			
1/2	3.74	2.63	4 × Ø0.62	0.79	0.62	17.28			
½ FB	3.74	2.63	4 × Ø0.62	0.75	0.67	22.56			
1	4.92	3.50	4 × Ø0.75	0.91	1.05	22.8			
1 FB	4.92	3.50	4 × Ø0.75	0.87	1.01	27.64			
1½	6.10	4.50	4 × Ø0.88	1.02	1.61	27.85			
1½ FB	6.10	4.50	4 × Ø0.88	0.94	1.4	32.32			
2	6.50	5.00	8 × Ø0.75	1.1	2.07	32.64			
2 FB	6.50	5.00	8 × Ø0.75	1.69	2.16	47.7			
3	8.27	6.63	8 × Ø0.88	1.65	3.07	47.68			

1) DN 3/8" with DN  $\frac{1}{2}$ " flanges as standard;

1.4301 (304), w	Flange according to ASME B16.5: Class 600 1.4301 (304), wetted parts: titanium Order code for "Process connection", option ACW										
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]					
3/8 1)	3.74	2.63	4 × Ø0.62	0.79	0.54	15.87					
1/2	3.74	2.63	4 × Ø0.62	0.79	0.54	17.28					
½ FB	3.74	2.63	4 × Ø0.62	0.87	0.67	22.56					
1	4.92	3.50	4 × Ø0.75	0.91	0.96	22.8					
1 FB	4.92	3.50	4 × Ø0.75	0.98	1.01	27.64					
1½	6.10	4.50	4 × Ø0.88	1.1	1.5	27.85					
1½ FB	6.10	4.50	4 × Ø0.88	1.14	1.4	32.32					
2	6.50	5.00	8 × Ø0.75	1.3	1.94	32.8					
2 FB	6.50	5.00	8 × Ø0.75	1.81	2.16	47.7					

1.4301 (304), w	Flange according to ASME B16.5: Class 600 1.4301 (304), wetted parts: titanium  Order code for "Process connection", option ACW						
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]	
3	8.27	6.63	8 × Ø0.88	2.09	2.9	48.15	


FB = Full bore

Surface roughness (flange): Ra 126 to 248  $\mu in$ 

DN 3/8" with DN  $\frac{1}{2}$ " flanges as standard;

#### **Clamp connections**

#### Tri-Clamp



Length tolerance for dimension L in inch:  $+0.06\ /\ -0.08$ 

Tri-Clamp ( ≥ 1"), DIN 11866 series C  Titanium  Order code for "Process connection", option FTW								
DN [in]	Clamp [in]	A [in]	B [in]	L [in]				
3/8	1	1.98	0.87	16.77				
1/2	1	1.98	0.87	18.19				
½ FB	see ¾"Tri-Clamp connection							
1	1	1.98	0.87	23.7				
1 FB	1	1.98	0.87	28.76				
11/2	1 ½	1.98	1.37	28.76				
1½ FB	1 ½	1.98	1.37	33.46				
2	2	2.52	1.87	33.46				
2 FB <sup>1)</sup>	2 ½	3.05	2.37	49.92				
3	3	3.58	2.87	49.92				

3A version available: order code for "Additional approval", option LP in conjunction with  $Ra_{max} = 30 \ \mu in$ : order code for "Measuring tube material", option CB or  $Ra_{max} = 15 \ \mu in$ : order code for "Measuring tube material", option CD

Order code for "Process connection", option FRW

## 3/4" Tri-Clamp, DIN 11866 series C

Titanium

Order code for "Process connection", option FEW

DN [in]	Clamp [in]	A [in]	B [in]	L [in]
3/8	3/4	0.98	0.63	16.77
1/2	3/4	0.98	0.63	18.19
½ FB	3/4	0.98	0.63	23.7

FB = Full bore

3A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max} = 30 \mu in$ : order code for "Measuring tube material", option CB or

 $Ra_{max} = 15 \mu in$ : order code for "Measuring tube material", option CD

#### 1/2" Tri-Clamp, DIN 11866 series C Titanium Order code for "Process connection", option FBW DN Clamp В L [in] [in] [in] [in] [in] 3/8 0.98 0.37 16.77 0.98 0.37 18.19

3A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max}$  = 30  $\mu in$ : order code for "Measuring tube material", option CB or

 $Ra_{max} = 15 \mu in$ : order code for "Measuring tube material", option CD

½         FEC         ¾         0.98         0.62           ½ FB         FEE         1         1.99         0.87	
½         FEC         ¾         0.98         0.62           ½ FB         FEE         1         1.99         0.87	L [in]
½ FB FEE 1 1.99 0.87	16.77
	18.19
1 100 007	23.7
1   FEE   1   1.99   0.87	23.7
1 FB FEG 1½ 1.99 1.37	28.76
1½ FEG 1½ 1.99 1.37	28.76
1½ FB FEJ 2 2.52 1.87	33.46
2 FEJ 2 2.52 1.87	33.46
2 FB FEL 2 ½ 3.05 2.37	49.94
2 FB FEM 3 3.58 2.87	49.94
3 FEL 2½ 3.05 2.37	49.94
3 FEM 3 3.58 2.87	49.94

FB = Full bore

3A version available: order code for "Additional approval", option LP in conjunction with


 $Ra_{max} = 30 \mu in$ : order code for "Measuring tube material", option CB or

 $Ra_{max} = 15 \mu in$ : order code for "Measuring tube material", option CD

Additional information on "Eccentric clamps"

#### Couplings

#### Thread SMS 1145




Length tolerance for dimension L in inch: +0.06 / -0.08

<b>Titanium</b> Order code for "Process connection", option <b>SAW</b>								
DN [in]	A [in]	B [in]	L [in]					
3/8	Rd 40 × 1/6	0.89	16.77					
1/2	Rd 40 × 1/6	0.89	18.19					
1	Rd 40 × 1/6	0.89	23.7					
1 FB	Rd 40 × 1/6	0.89	29.02					
1½	Rd 60 × 1/6	1.4	29.07					
1½ FB	Rd 60 × 1/6	1.4	33.78					
2	Rd 70 × 1/6	1.91	33.78					
2 FB	Rd 70 × 1/6	1.91	49.55					
3	Rd 98 × 1/6	2.83	49.94					

### Safety Barrier Promass 100

Top-hat rail EN 60715:

- TH 35 x 7.5
  TH 35 x 15




A	В	С	D
[mm]	[mm]	[mm]	[mm]
108	114.5	99	22.5

#### Accessories

Purge connections / secondary containment monitoring

Order code for "Sensor options", option CH



A0003321

DN	G	Н	L
[in]	[in]	[in]	[in]
3/8	½-NPT	3.57	4.80
1/2	½-NPT	3.57	6.22
½ FB	½-NPT	3.57	6.22
1	½-NPT	3.57	11.66
1 FB	½-NPT	3.57	11.66
1½	½-NPT	4.07	15.44
1½ FB	½-NPT	4.07	15.44
2	½-NPT	4.64	19.22
2 FB	½-NPT	5.73	32.40
3	½-NPT	5.73	32.40

# Weight

#### **Compact version**

Weight in SI units

All values (weight) refer to devices with EN/DIN PN 40 flanges. Weight information in [kg].

DN [mm]	Weight [kg]
8	11
15	13
15 FB	19
25	20
25 FB	39
40	40
40 FB	65
50	67
50 FB	118

DN [mm]	Weight [kg]
80	122
FB = Full bore	

#### Weight in US units

All values (weight) refer to devices with EN/DIN PN 40 flanges. Weight information in [lbs].

DN [in]	Weight [lbs]
3/8	24
1/2	29
½ FB	42
1	44
1 FB	86
1½	88
1½ FB	143
2	148
2 FB	260
3	269
FB = Full bore	

#### **Safety Barrier Promass 100**


49 g (1.73 ounce)

#### Materials

#### Transmitter housing

- Order code for "Housing", option A "Compact, aluminum coated": Aluminum, AlSi10Mq, coated
- Order code for "Housing", option B "Compact, hygienic, stainless": Hygienic version, stainless steel 1.4301 (304)
- Order code for "Housing", option C "Ultra-compact, hygienic, stainless": Hygienic version, stainless steel 1.4301 (304)
- Window material for optional local display ( $\rightarrow$   $\triangleq$  82):
  - For order code for "Housing", option A: glass
  - For order code for "Housing", option **B** and **C**: plastic

#### Cable entries/cable glands



A00206/

#### $\blacksquare$ 33 Possible cable entries/cable glands

- 1 Cable entry in transmitter housing with internal thread M20 x 1.5
- 2 Cable gland M20 x 1.5
- 3 Adapter for cable entry with internal thread G  $\frac{1}{2}$ " or NPT  $\frac{1}{2}$ "

80

Order code for "Housing", option A "Compact, coated aluminum"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Nickel-plated brass
Adapter for cable entry with internal thread G ½"	
Adapter for cable entry with internal thread NPT ½"	

Order code for "Housing", option B "Compact, hygienic, stainless"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Stainless steel, 1.4404 (316L)
Adapter for cable entry with internal thread G ½"	
Adapter for cable entry with internal thread NPT ½"	

#### Device plug

Electrical connection	Material
Plug M12x1	<ul> <li>Socket: Stainless steel, 1.4404 (316L)</li> <li>Contact housing: Polyamide</li> <li>Contacts: Gold-plated brass</li> </ul>

#### Sensor housing

- Acid and alkali-resistant outer surface
- Stainless steel 1.4301 (304)

#### Measuring tubes

Grade 9 titanium

#### **Process connections**

- Flanges according to EN 1092-1 (DIN 2501) / according to ASME B16.5/ according to JIS:
  - Stainless steel 1.4301 (304)
  - Wetted parts: Grade 2 titanium
- All other process connections:
   Grade 2 titanium

List of all available process connections  $\rightarrow \triangleq 82$ 

#### Seals

Welded process connections without internal seals

#### **Safety Barrier Promass 100**

Housing: Polyamide

#### Process connections

- Fixed flange connections:
  - EN 1092-1 (DIN 2501) flange
  - EN 1092-1 (DIN 2512N) flange
  - ASME B16.5 flange
  - JIS B2220 flange
  - DIN 11864-2 Form A flange, DIN11866 series A, flat flange
- Clamp connections

Tri-Clamp (OD tubes), DIN 11866 series C

- Excentric clamp connection:
  - Excen. Tri-Clamp, DIN 11866 series C
- Threaded hygienic connection:
  - DIN 11851 threaded hygienic connection, DIN11866 series A
  - SMS 1145 threaded hygienic connection
  - ISO 2853 threaded hygienic connection, ISO2037
  - DIN 11864-1 Form A threaded hygienic connection, DIN11866 series A



#### Surface roughness

All data relate to parts in contact with fluid. The following surface roughness quality can be ordered.

- Not polished
- $Ra_{max} = 0.76 \mu m (30 \mu in)$
- $Ra_{max} = 0.38 \mu m (15 \mu in)$

## **Operability**

#### Operating concept

#### Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnostics
- Expert level

#### Quick and safe commissioning

- Individual menus for applications
- Menu guidance with brief explanations of the individual parameter functions

#### Reliable operation

- Operation in the following languages:
  - Via "FieldCare" operating tool:
    - English, German, French, Spanish, Italian, Chinese, Japanese
  - Via integrated Web browser (only available for device versions with HART, PROFIBUS DP, PROFINET and EtherNet/IP):
    - English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech, Swedish, Korean
- Uniform operating philosophy applied to operating tools and Web browser
- If replacing the electronic module, transfer the device configuration via the plug-in memory (HistoROM DAT) which contains the process and measuring device data and the event logbook. No need to reconfigure.

For devices with Modbus RS485, the data recovery function is implemented without the plug-in memory (HistoROM DAT).

#### Efficient diagnostics increase measurement availability

- Troubleshooting measures can be called up via the operating tools and Web browser
- Diverse simulation options
- Status indicated by several light emitting diodes (LEDs) on the electronic module in the housing compartment

### Local display

A local display is only available for device versions with the following communication protocols: HART, PROFIBUS-DP, PROFINET, EtherNet/IP

The local display is only available with the following device order code: Order code for "Display; Operation", option **B**: 4-line; lit, via communication


#### Display element

- 4-line liquid crystal display with 16 characters per line.
- White background lighting; switches to red in event of device errors.
- Format for displaying measured variables and status variables can be individually configured.
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F). The readability of the display may be impaired at temperatures outside the temperature range.

#### Remote operation

#### Via HART protocol

This communication interface is available in device versions with a HART output.




A0016948

■ 34 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 VIATOR Bluetooth modem with connecting cable
- 7 Transmitter

#### Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




A002090

■ 35 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Measuring device

#### Via Ethernet-based fieldbus

This communication interface is available in device versions with EtherNet/IP.




A00169

■ 36 Options for remote operation via Ethernet-based fieldbus

- 1 Control system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Add-on Profile Level 3 for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 4 Ethernet switch
- 5 Measuring device

#### Via PROFINET network

This communication interface is available in device versions with PROFINET.



A002654

■ 37 Options for remote operation via PROFINET network

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device


#### Service interface

#### Via service interface (CDI-RJ45)

This communication interface is present in the following device version:

- Order code for "Output", option **B**: 4-20 mA HART, pulse/frequency/switch output
- Order code for "Output", option L: PROFIBUS DP
- Order code for "Output", option N: EtherNet/IP
- Order code for "Output", option **R**: PROFINET


#### **HART**



A0016926

- 38 Connection for the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output
- 1 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


#### PROFIBUS DP



A0021270

- 39 Connection for order code for "Output", option L: PROFIBUS DP
- 1 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

#### EtherNet/IP




A0016940

#### ■ 40 Connection for order code for "Output", option N: EtherNet/IP

- 1 Service interface (CDI -RJ45) and EtherNet/IP interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

#### **PROFINET**



A0016940


■ 41 Connection for order code for "Output", option R: PROFINET

- Service interface (CDI -RJ45) and PROFINET interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

#### Via service interface (CDI)

This communication interface is present in the following device version: Order code for "Output", option  ${\bf M}$ : Modbus RS485

#### Modbus RS485



\_\_\_\_\_

- 1 Service interface (CDI) of the measuring device
- 2 Commubox FXA291
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

## Certificates and approvals

#### CE mark

The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied.

Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

#### C-Tick symbol

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

#### Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.

#### ATEX/IECEx

Currently, the following versions for use in hazardous areas are available:

#### Ex ia

Category (ATEX)	Type of protection
II2G	Ex ia IIC T6T1 Gb
II2G	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb
II1/2G, II2D	Ex ia IIC T6T1 Ga/Gb or Ex ia IIB T6T1 Ga/Gb Ex tb IIIC Txx °C Db
II2G, II2D	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb Ex tb IIIC Txx °C Db

#### Ex nA

Category (ATEX)	Type of protection
II3G	Ex nA IIC T6T1 Gc or Ex nA IIC T5-T1 Gc

#### $_{C}CSA_{US}$

Currently, the following versions for use in hazardous areas are available:

IS (Ex i)

- Class I Division 1 Groups ABCD
- Class II Division 1 Groups EFG and Class III

NI (Ex nA

Class I Division 2 Groups ABCD

#### Sanitary compatibility

- 3-A approval
- EHEDG-tested

#### **HART** certification

#### **HART** interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability)

#### **Certification PROFIBUS**

#### **PROFIBUS** interface

The measuring device is certified and registered by the PROFIBUS User Organization (PNO). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with PROFIBUS PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

#### **Certification PROFINET**

#### **PROFINET** interface

The measuring device is certified and registered by the PNO (PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
  - Test specification for PROFINET devices
  - PROFINET Security Level 1 Net load test
- The device can also be operated with certified devices of other manufacturers (interoperability)

#### EtherNet/IP certification

The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with the ODVA Conformance Test
- EtherNet/IP Performance Test
- EtherNet/IP PlugFest compliance
- The device can also be operated with certified devices of other manufacturers (interoperability)

#### Modbus RS485 certification

The measuring device meets all the requirements of the MODBUS/TCP conformity test and has the "MODBUS/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out and is certified by the "MODBUS/TCP Conformance Test Laboratory" of the University of Michigan.

#### Pressure Equipment Directive

The devices can be ordered with or without a PED approval. If a device with a PED approval is required, this must be explicitly stated in the order. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary.

- With the PED/G1/x (x = category) marking on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements" specified in Annex I of the Pressure Equipment Directive 97/23/EC.
- Devices bearing this marking (PED) are suitable for the following types of medium:
  - Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to 0.5 bar (7.3 psi)
  - Unstable gases
- Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Art.3 Section 3 of the Pressure Equipment Directive 97/23/EC. The range of application is indicated in tables 6 to 9 in Annex II of the Pressure Equipment Directive.

# Other standards and guidelines

■ EN 60529

Degrees of protection provided by enclosures (IP code)

■ IEC/EN 60068-2-6

Environmental influences: Test procedure - Test Fc: vibrate (sinusoidal).

■ IEC/EN 60068-2-31

Environmental influences: Test procedure - Test Ec: shocks due to rough handling, primarily for devices.

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements

■ IEC/EN 61326

Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).

■ NAMUR NE 21

Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment

■ NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

■ NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

■ NAMUR NE 80

The application of the pressure equipment directive to process control devices

■ NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices

■ NAMUR NE 107

Self-monitoring and diagnosis of field devices

■ NAMUR NE 131

Requirements for field devices for standard applications

NAMUR NE 132
 Coriolis mass meter

# Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select your country → Products → Select measuring technology, software or components → Select the product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product opens.
- From your Endress+Hauser Sales Center: www.addresses.endress.com



#### Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

# Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: <a href="https://www.endress.com">www.endress.com</a>.



Detailed information on the application packages:

- Special Documentation for the device
- Special Documentation for the device

#### **Heartbeat Technology**

Package	Description
Heartbeat Verification +Monitoring	Heartbeat Monitoring Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to:  Draw conclusions - using these data and other information - about the impact process influences (such as corrosion, abrasion, buildup etc.) have on the measuring performance over time.  Schedule servicing in time.  Monitor the process or product quality, e.g. gas pockets.
	Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment".  Functional testing in the installed state without interrupting the process.  Traceable verification results on request, including a report.  Simple testing process via local operation or other operating interfaces.  Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.  Extension of calibration intervals according to operator's risk assessment.

#### Concentration

Package	Description
Concentration measurement and special density	Calculation and outputting of fluid concentrations Many applications use density as a key measured value for monitoring quality or controlling processes. The device measures the density of the fluid as standard and makes this value available to the control system.  The "Special Density" application package offers high-precision density measurement over a wide density and temperature range particularly for applications subject to varying process conditions.
	With the help of the "Concentration Measurement" application package, the measured density is used to calculate other process parameters:  Temperature-compensated density (reference density).  Percentage mass of the individual substances in a two-phase fluid. (Concentration in %).  Fluid concentration is output with special units ("Brix, "Baumé, "API, etc.) for standard applications.
	The measured values are output via the digital and analog outputs of the device.

#### Viscosity

Package	Description
Viscosity measurement	In-line and real-time viscosity measurement Promass I with the "Viscosity" application package also measures the real-time viscosity of the fluid directly in the process, in addition to measuring the mass flow/volume flow/ temperature and density.
	The following viscosity measurements are performed on liquids:  Dynamic viscosity  Kinematic viscosity  Temperature-compensated viscosity (kinematic and dynamic) in relation to the reference temperature
	Viscosity measurement can be used for Newtonian and non-Newtonian applications and supplies accurate measured data irrespective of the flow, even under difficult conditions.

90

## Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

### Device-specific accessories

#### For the sensor

Accessories	Description
Heating jacket	Is used to stabilize the temperature of the fluids in the sensor.  Water, water vapor and other non-corrosive liquids are permitted for use as fluids.  If using oil as a heating medium, please consult with Endress+Hauser.  For details, see Operating Instructions BA00099D

# Communication-specific accessories

Accessories	Description		
Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface.  For details, see "Technical Information" TI00404F		
Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop.  For details, see the "Technical Information" document TI405C/07		
HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.  For details, see "Technical Information" TI00429F and Operating Instructions BA00371F		
Wireless HART adapter SWA70	Is used for the wireless connection of field devices.  The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity.  For details, see Operating Instructions BA00061S		
Fieldgate FXA320	Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser.  For details, see "Technical Information" TI00025S and Operating Instructions BA00053S		
Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser.  For details, see "Technical Information" TI00025S and Operating Instructions BA00051S		
Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the <b>non-Ex area</b> .  For details, see Operating Instructions BA01202S		
Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the <b>non-Ex area</b> and the <b>Ex area</b> .  For details, see Operating Instructions BA01202S		


#### Service-specific accessories

Accessories	Description			
Applicator	Software for selecting and sizing Endress+Hauser measuring devices:  Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections.  Graphic illustration of the calculation results			
	Administration, documentation and access to all project-related data and parameters throughout the entire life cycle of a project.			
	Applicator is available:  Via the Internet: https://wapps.endress.com/applicator  On CD-ROM for local PC installation.			
W@M	Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle.  The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records.  W@M is available:  Via the Internet: www.endress.com/lifecyclemanagement On CD-ROM for local PC installation.			
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. Busing the status information, it is also a simple but effective way of checking their status and condition.  For details, see Operating Instructions BA00027S and BA00059S			
DeviceCare	Tool for connecting and configuring Endress+Hauser field devices.			
	For details, see Innovation brochure IN01047S			
Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop.  For details, see "Technical Information" TI00405C			

#### System components

Accessories	Description
Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.  For details, see "Technical Information" TI00133R and Operating Instructions
	BA00247R
iTEMP	The temperature transmitters can be used in all applications and are suitable for the measurement of gases, steam and liquids. They can be used to read in the fluid temperature.
	For details, see "Fields of Activity", FA00006T

# Supplementary documentation



- The *W@M Device Viewer*: Enter the serial number from the nameplate (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

#### Standard documentation

#### **Brief Operating Instructions**



 $\hfill Brief$  Operating Instructions containing the most important information for standard commissioning are supplied with the device.

#### **Operating Instructions**

	Documentation code				
Measuring device	HART	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET
Promass I 100	BA01190D	BA01251D	BA01058D	BA01066D	BA01429D

#### Description of device parameters

	Documentation code				
Measuring device	HART	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET
Promass 100	GP01033D	GP01034D	GP01035D	GP01036D	GP01037D

#### Supplementary devicedependent documentation

#### **Safety Instructions**

Content	Documentation code
ATEX/IECEx Ex i	XA00159D
ATEX/IECEx Ex nA	XA01029D
cCSAus IS	XA00160D
INMETRO Ex i	XA01219D
INMETRO Ex nA	XA01220D
NEPSI Ex i	XA01249D
NEPSI Ex nA	XA01262D

#### **Special Documentation**

Content	Documentation code
Information on the Pressure Equipment Directive	SD00142D
Modbus RS485 Register Information	SD00154D
Concentration Measurement	SD01152D
Viscosity Measurement	SD01151D
Heartbeat Technology	SD01153D

#### **Installation Instructions**

Contents	Documentation code
Installation Instructions for spare part sets	Specified for each individual accessory

# Registered trademarks

Registered trademark of the HART Communication Foundation, Austin, USA

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

#### Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

#### EtherNet/IP<sup>TM</sup>

Trademark of ODVA, Inc.

#### **PROFINET®**

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

#### Microsoft®

Registered trademark of the Microsoft Corporation, Redmond, Washington, USA

#### TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA

# Applicator®, FieldCare®, DeviceCare®, Field Xpert™, HistoROM®, TMB®, Heartbeat Technology™

Registered or registration-pending trademarks of the Endress+Hauser Group





www.addresses.endress.com