# Technical Information Liquistation CSF28

## Automatic stationary sampler for liquid media



#### Applications

Liquistation CSF28 is suitable for time- and flow-controlled sampling in the following applications:

Municipal and industrial wastewater treatment plants:

- Self-monitoring
- Process monitoring
- Monitoring of dischargers
- Monitoring of wastewater systems

Authorities and water management offices:

- Water pollution control and water quality
- Monitoring of dischargers

#### Your benefits

- Intended purpose: Application-specific operation, e.g. filling capabilities
- Easy commissioning: Quick customization to monitoring task with wizard-guided setup
- Reliable and robust sampling: Keep your process running without interruptions or variations thanks to time-tested components and comprehensive diagnostic capabilities at the device for maintenance purposes
- Reduced maintenance: Liquistation CSF28 enables fast and easy cleaning and maintenance thanks to the simple and tool-free removal of parts in contact with the medium
- Basic monitoring functions: Definition of time- or flow-controlled sampling routines adapted to your requirements, simple monitoring without event sampling
- **Cutting-edge cooling technology:** Benefit from sustainable and environmentally friendly technologies to store your samples
- Full compliance: Automatic water sampling in full compliance with all the relevant national and international standards such as ISO 5667



# Table of contents

Function and system design         Device principle         Sampling unit         Dependability	<b>3</b> • 5 • 9
Input	<b>10</b> 10 10 10 10
Output Communication Relay outputs	<b>10</b> 10 11
Protocol-specific data	<b>11</b> 11
Power supply	<b>11</b> 11 11 11 11 11
Performance characteristics	<ul> <li>12</li> </ul>
Mounting	<b>13</b> 13 13
Environment	<b>14</b> 14 14 14 14 14 14
Process	<b>14</b> 14 14 14 14
Mechanical construction Dimensions Weight	<b>15</b> 15 15

Materials	15
Operability	17 17 17 18 18 18
Certificates and approvals	19
Ordering information Product page Product Configurator Scope of delivery	<b>20</b> 20 20 20
Accessories	21

## Function and system design

#### **Device** principle

#### Mode of operation with a vacuum pump

#### Sampling takes place in four steps:



#### 1. Blow clear

└ The vacuum pump blows the suction line clear via the dosing system.

2. Intake

└ The "Airmanager" (pneumatic control unit) switches the air path of the vacuum pump to "intake". The sample is drawn into the dosing beaker until it reaches the conductivity probes of the dosing system.

#### 3. Dose

└ The intake process ends. Depending on the position of the dosing tube (item D), the excess sample liquid flows back to the sampling point.

#### 4. Drain

└ The hose clamp is opened and the sample is drained into the sample bottle.

#### Dosing system with conductive sample sensor



#### ■ 1 Conductive dosing system

- *1* Conductivity sensor 1 (common electrode)
- 2 Conductivity sensor 2 (safety electrode)
- *3 Conductivity sensor 3 (standard electrode)*
- 4 Insulation
- 5 Measuring jug (plastic version)
- 6 Graduated dosing tube, white and blue scale

#### Level detection principle

When the sample is drawn in, the sample level reaches conductivity sensors 1 and 3. As a result, the system detects that the measuring jug is filled and the intake process is stopped. If sensor 3 fails or is very dirty, a safety shutdown is performed by conductivity sensor 2. This patented sample detection method prevents vacuum pump failure due to flooding and enables predictive maintenance information to be displayed.

#### $\mathbf{f}$

#### Sample dosing without/with pressure

Sample dosing without pressure is the (factory) setting for all standard applications in which the sample medium is taken from an open channel or a gravity line. The excess sample can flow back under atmospheric pressure. Sample dosing with pressure is selected for applications involving a low suction height, small sampling volumes or high-viscosity samples. In these cases, the sample medium cannot flow back on its own. The excess sample is forced out of the measuring jug under pressure and back to the sampling point. The sample volume is set by adjusting the dosing tube. The white "A" scale applies if dosing without pressure, and the blue "B" scale applies if dosing with pressure.

#### Mode of operation with a peristaltic pump



Sampling steps with a peristaltic pump

#### Sampling takes place in three steps:

#### 1. Rinse

└ The peristaltic pump runs in reverse and forces medium back to the sampling point.

#### 2. Intake

└ The peristaltic pump runs forward and draws in medium. If the medium detection system detects the sample, the pump is controlled by the flow and the specified sample volume is calculated automatically.

3. Drain

└ The pump runs in reverse again and forces the medium back to the sampling point.

One advantage for obtaining a representative sample is the possibility of rinsing the suction line several times: Medium is initially drawn in until the medium detection function responds, then the pump switches and forces the medium back to the sampling point. This process can be repeated a maximum of three times. The sample is then taken as described.



- Image: Book of the second s
- 1 Pump tube
- 3 Pump rollers
- 4 Medium detection system (patented)

The pump rollers deform the hose, thereby causing a negative pressure and the suction effect. The medium detection system is based on a pressure sensor which detects the difference between a pipe that is filled and not filled. Thanks to a patented process for automatically detecting the suction height, the user does not need to enter the suction height or suction line length. The self-learning software guarantees a constant sample volume.

Sampling unit

#### Sampler Liquistation CSF28

Depending on the version, a complete sampling unit for open channels comprises:

- Controller with display, soft keys and navigator
- Vacuum or peristaltic pump for sampling
- PE sample bottles for sample preservation
- Sampling chamber temperature regulator for safe sample storage
- Suction line with suction head



Example of a Liquistation, version with vacuum pump



☑ 5 Example of a Liquistation, version with peristaltic pump

#### Sample distribution

The sampler offers a wide range of bottle combinations and distribution versions. The versions can be changed or replaced easily without the need for special tools.

#### Sample preservation

The sample bottles are located in the sample compartment. This is fitted with a seamless plastic dish to ensure easy cleaning. All parts that transport medium (distribution arm, dosing system...) can be removed and cleaned easily without the need for tools.

- 1 Controller
- 2 Dosing compartment door
- 3 Suction line connection
- 4 Sampling chamber door
- 5 Sample bottles, e.g. 2 x 12 bottles, PE, 1 liter
- 6 Bottle trays (depending on sample bottles selected)
- 7 Distribution plate (depending on sample bottles selected)
- 8 Distribution arm
- 9 Vacuum system, e.g. Dosing system with conductive sample sensor
- 1 Controller
- 2 Dosing compartment door
- 3 Suction line connection
- 4 Sampling chamber door
- 5 Sample bottles, e.g. 2 x 12 bottles, PE, 1 liter
- 6 Bottle trays (depending on sample bottles selected)
- 7 Distribution plate (depending on sample bottles selected)
- 8 Distribution arm
- 9 Peristaltic pump



A0029681

Bottle groups and distribution versions with the number of bottles.



#### Sampling control

#### Intake speed with different suction lines



 $\blacksquare 6$  Intake speed in m/s (ft/s) with suction height in m (ft)

- A Intake speed as per Ö 5893; US EPA
- B Intake speed as per EN 25667, ISO 5667
- 1 ID 10 mm (3/8 in) vacuum pump
- 2 ID 13 mm (1/2 in) vacuum pump
- 3 ID 10 mm (3/8 in) peristaltic pump

#### Sample temperature regulation

The temperature of the sample compartment can be adjusted using the controller. The factory setting is 4  $^{\circ}C$  (39  $^{\circ}F$ ). The current temperature is shown on the display and is recorded in the internal data logger once the user has successfully run through the Commissioning Wizard.

The vaporizer and defrost heater are integrated in a special housing such that they are protected against corrosion and damage. The compressor and the condenser are located in the upper section of the sampler. They can be easily accessed by removing the upper rear panel (for maintenance purposes).

#### Sampler housing

The housing is made from high-grade plastic ASA+PC VO. This material is highly resistant to external influences and is very suitable for outdoor installations.

Dependability	Maintainability	
	Memory	
	<ul> <li>Independent, integrated ring memories (FIFO)</li> </ul>	
	<ul> <li>an analog value (e.g. temperature, flow measurement)</li> </ul>	
	<ul> <li>events (e.g. power failure)</li> </ul>	
	<ul> <li>Sample statistics (e.g. sampling volume, filling times, bottle assignment)</li> </ul>	
	<ul> <li>Program memory: max. 3 programs</li> </ul>	
	• Data logbooks: A = A = 1 + 1 + 2 + 2 + 2 + 2 + 2 + 2 + 2 + 2 +	
	<ul> <li>Adjustable scan time: 1 to 3600 s (1 n)</li> <li>Max 9 data logbooks</li> </ul>	
	<ul> <li>IVIAL O GATA TOYDOOKS</li> <li>150 000 entries per logbook</li> </ul>	
	<ul> <li>Graphic display (load curves) or numerical list</li> </ul>	
	<ul> <li>Calibration logbook: max. 75 entries</li> </ul>	
	<ul> <li>Hardware logbook:</li> </ul>	
	<ul> <li>Hardware configuration and modifications</li> </ul>	
	<ul> <li>Max. 125 entries</li> </ul>	
	<ul> <li>Version logbook:</li> </ul>	
	<ul> <li>Including software updates</li> </ul>	
	• Max. 50 entries	
	<ul> <li>Operations logbook: max. 250 entries</li> <li>Diagnostic logbook: max. 250 entries</li> </ul>	
	<ul> <li>Diagnostic logbook. max. 250 entries</li> </ul>	
	Manuel Data lankasti 4/Chassalat OK	
	riend/Data logbook 1/Snow plot OK	
	$\Lambda_{n}$ *	
	26.11.2010 30.11.2010 05.12.2010 23:51:07 11:33:16 23:13:01	
	25.1 °C	
	X	
		A0024359
	7 Data logbook: graphic display	
	FieldCare	

Configuration and asset management software based on FDT/DTM technology

- Complete device configuration when connected via FXA291 and service interface
- Logbooks can be downloaded in CSV format

#### SD card

- The exchangeable storage medium enables:
- Quick and easy software updates and upgrades
- Data storage of internal device memory (e.g. logbooks)
- Transfer of complete configurations to a device with an identical setup (backup function)
- Transfer of configurations without the device designation to devices with an identical setup (copy function)

#### Security

#### Real-time clock

The device has a real-time clock, which is backed up by a button cell in the event of a power failure. This ensures that the device continues to keep the correct time and date if it is restarted and that the time stamp for the logbooks is correct.

#### Data security

All settings, logbooks etc. are stored in a non-volatile memory to ensure that the data are retained even in the event of a disruption to the power supply.

# Input

Types of input	1 analog input
	1 binary input
Binary input, passive	Span
	- 12 to 30 V, galvanically isolated
	Signal characteristics
	Signal characteristics
	Minimum pulse width: 100 ms
	Signal edge
	Low-high
Temperature input	Measuring range
	-30 to 70 °C (-20 to 160 °F)
	A source of
	Accuracy
	± 0.5 K
	Type of input
	Pt1000
Analog input, passive/active	Span
	0/4 to 20 mA, galvanically isolated
	Accuracy
	Actuacy
	±0.5 % of measuring range

# Output

Communication

- 1 service interface
- Commubox FXA291 (accessory) required for communication with the PC

#### **Relay outputs**

#### Electrical specification

**Relay type** 2 x changeover contact, coupled with binary output

**Maximum load** All other relays: 2.0 A

#### Relay switching capacity

Relay coupled with binary output

Switching voltage	Load (max.)	Switching cycles (min.)
230 V AC, $\cos \Phi = 0.8$ to 1	5 A	100,000
24 V DC, L/R = 0 to 1 ms	5 A	100,000

Minimum load (typical)

- min. 100 mA at 5 V DC
- min. 1 mA at 24 V DC
- min. 5 mA at 24 V AC
- min. 1 mA at 230 V AC

## Protocol-specific data

#### Web server

The web server enables full access to the device configuration, measured values, diagnostic messages, logbooks and service data via standard WiFi/WLAN/LAN/GSM or 3G routers with a user-defined IP address.

TCP port	80
Supported features	<ul> <li>Remote-controlled device configuration</li> <li>Save/restore device configuration (via SD card)</li> <li>Logbook export (file format: CSV)</li> <li>Access to web server via DTM or Internet Explorer</li> </ul>

## Power supply

Supply voltage	100 to 120/200 to 240 V AC ±10 %, 50/60 Hz
Power consumption	<ul> <li>Version with vacuum pump: 290 VA</li> <li>Version with peristaltic pump: 290 VA</li> </ul>
Electrical connection	See the "Electrical connection" section ()
Cable entries	1 x M25, 1 x M20 cable gland
	Permitted cable diameter: • M20x1.5 mm: 7 to 13 mm (0.28 to 0.51") • M25x1.5 mm: 9 to 17 mm (0.20 to 0.67")
Mains fuse	T3.15A (for 230V power supply)

Sampling methods	Vacuum pump: Time-paced  Flow-paced		
	Peristaltic pump: Time-paced  Flow-paced		
	<ul> <li>Flow proportional sampling/time override (CTVV)</li> </ul>		
Dosing volume	<b>Vacuum pump:</b> 20 to 350 ml (0.7 to 12 fl.oz.)		
	<b>Peristaltic pump:</b> 10 to 10000 ml (0.3 to 340 fl.oz.)		
	The dosing accuracy and the repeatability of a sample volume < 20 ml (0.7 fl.oz) can vary, depending on the specific application.		
Dosing accuracy	<ul> <li>Vacuum pump: ± 5 ml (0.17 fl.oz.) or 5 % of the set volume</li> <li>Peristaltic pump: ± 5 ml (0.17 fl.oz.) or 5 % of the set volume</li> </ul>		
Repeatability	5 %		
Intake speed	> 0.5 m/s (> 1.6 ft/s) for $\le$ 13 mm (1/2 in) ID, as per EN 25667, ISO 5667, CEN 16479-1 > 0.6 m/s (> 1.9 ft/s) for 10 mm (3/8 in) ID, as per Ö 5893; US EPA		
Suction height • Vacuum pump: Max. 6 m (20 ft) • Peristaltic pump: Max. 8 m (26 ft)			
Hose length	Max. 30 m (98 ft)		
Temperature control	<b>Temperature sensors:</b> Sampling compartment temperature		
	<ul> <li>Cooling module:</li> <li>Sample temperature range: 2 to 20 °C (36 to 68 °F) Factory setting: 4 °C (39 °F)</li> <li>Automatic defrost system</li> <li>Cooling rate in accordance with Ö 5893 (Austrian standard): 4 liters of water at 20 °C (68 °F) cool down to 4 °C (39 °F) in less than 210 minutes</li> <li>Temperature constancy of sample at 4 °C (39 °F) at an operating temperature range of -15 to 40 °C (5 to 105 °F)</li> </ul>		

# Performance characteristics

## Mounting





🛃 8 Foundation plan. Unit of measurement mm (in)

- Α Fasteners (4 x M10)
- В Cable inlet
- Outlet for condensate and overflow > DN 50 С
- Sample supply from below > DN 80 Dimensions of Liquistation D
- ---

#### Mounting conditions



🛃 9 Liquistation mounting conditions

#### Mounting conditions

Route the suction line with a downward gradient to the sampling point.

Never mount the sampler in a place where it is exposed to aggressive gases.

#### Mounting conditions

Avoid siphoning effects in the suction line.

Do not route the suction line with an upward gradient to the sampling point.

Note the following when erecting the device:

- Erect the device on a level surface.
- Connect the device securely to the surface at the fastening points.
- Protect the device against additional heating (e.g. heaters or direct sunlight).
- Protect the device against mechanical vibrations.
- Protect the device against strong magnetic fields.
- Make sure air can circulate freely at the side panels of the cabinet. Do not mount the device directly against a wall. Allow at least 150 mm (5.9 in.) from the wall to the left and right.
- Do not erect the device directly above the inlet channel of a wastewater treatment plant.

Ambient temperature range	With cooling module:	-20 to 40 °C (0 to 104 °F)
Storage temperature	–20 to 60 °C (–4 to 140 °F)	
Electrical safety	In accordance with EN 61010-1, protection class I, environment $\leq$ 2000 m (6500 ft) above MSL. T device is designed for pollution degree 2.	
Relative humidity	10 to 95%, not condensing	
Degree of protection	<ul> <li>Front dosing compartmen</li> <li>Rear dosing compartment</li> <li>Front panel with display (i</li> <li>Sample compartment: IP 5</li> </ul>	t: IP 54 IP 33 nternal): IP 65 4
	The IP protection ratings list degree of protection for the	ed above apply for individual sections of the overall device. The resulting overall device is IP33.
Electromagnetic compatibility (EMC)	Interference emission and interference immunity as per EN 61326-1:2013, Class A for Industry	

## **Environment**

### Process

Medium temperature range	2 to 50 °C (36 to 122 °F)
Process pressure range	Unpressurized, open channel (unpressurized sampling)
Medium properties	<b>Vacuum pump</b> Sample media has to be free of abrasive substances.
	<b>Peristaltic pump</b> Sample media has to be free of abrasive substances.
	Pay attention to the material compatibility of the wetted parts.
Process connection	<ul> <li>Vacuum pump: Intake hose ID 10 mm (3/8 in) and 13 mm (1/2 in)</li> <li>Peristaltic pump: Intake hose ID 10 mm (3/8 in)</li> </ul>

## Mechanical construction



🖻 10 Dimensions of Liquistation, plastic version. Unit of measurement mm (in)

A Suction line connection

Weight	Sampler version	Weight
	Plastic version with refrigeration	101 kg (223 lbs)

Materials

Non-wetted parts	
Cabinet housing	<b>Plastic ASA+PC V0</b> For industrial wastewater treatment plants with an aggressive atmosphere
Sample compartment inner lining	Plastic PP
Insulation	Plastic EPS "Neopor®"

Wetted parts	Vacuum pump	Peristaltic pump
Dosing tube	Plastic PP	-
Measuring jug cover	Plastic PP	-
Conductivity sensors	Stainless steel V4A (1.4404)	-
Measuring jug	РММА	-
Dosing system outflow hose	Silicone	-
Pump tube	-	Silicone
Distribution arm	Plastic PP	
Distribution arm cover	Plastic PE	
Distribution plate	Plastic PS	
Composite container/bottles	Plastic PE	
Intake hose	Plastic PVC, EPDM (depending on version	1)
Hose connection	Plastic PP	



Choose process seal depending on the application. Viton is recommended for standard applications involving watery samples.

Vacuum pump only		
Pneumatic hoses	Silicone	
Air Manager housing	PC	
Air Manager sealing plate	Silicone	
Pump head	Aluminum, anodized	
Pump membrane	EPDM	

## Operability

#### **Operating concept**

- The simple and structured operating concept sets new standards:
- Intuitive operation with the navigator and soft keys
- Fast configuration of application-specific measurement options
- Easy configuration and diagnosis thanks to plain-text display
- All languages that can be ordered are available in every device



#### Display

- Graphic display:
- Resolution: 240 x 160 pixel
- Back light with switch-off function
- Red display background for alarms alerts users to errors
- Transflective display technology for maximum contrast even in bright environments



#### 🖻 11 Example of start menu

#### Local operation



- LCD, illuminated (with red background in the event of an error)
- 160 x 240 pixels
- 4 operating keys (soft key function) and navigator (jog/shuttle and press/hold function)
- Menu-guided operation



Web server



• 12 Example of system integration via web server

Communication	<ul> <li>1 service interface</li> <li>Commubox FXA291 (accessory) required for communication with the PC</li> </ul>
Software	FieldCare

Storage of device settings in a databaseParameter configuration

## **Certificates and approvals**

Current certificates and approvals that are available for the product can be selected via the Product Configurator at <a href="https://www.endress.com">www.endress.com</a>:

- 1. Select the product using the filters and search field.
- 2. Open the product page.
- 3. Select **Configuration**.

Product page	www.endress.com/CSF28
Product Configurator	1. <b>Configure</b> : Click this button on the product page.
	2. Select <b>Extended selection</b> .
	3. Configure the device according to your requirements by selecting the desired option for each feature.
	└ In this way, you receive a valid and complete order code for the device.
	4. <b>Apply</b> : Add the configured product to the shopping cart.
	For many products, you also have the option of downloading CAD or 2D drawings of the selected product version.
	5. <b>Show details</b> : Open this tab for the product in the shopping cart.
	The link to the CAD drawing is displayed. If selected, the 3D display format is displayed along with the option to download various formats.
Scope of delivery	<ul> <li>The scope of delivery comprises:</li> <li>1 Liquistation CSF28 with: The ordered bottle configuration</li> <li>Accessories kit For peristaltic or vacuum pump: Hose adapter for suction line with various angles (straight, 90°), Allen screw (for version with vacuum pump only)</li> <li>1 printed copy of the Brief Operating Instructions in the language ordered</li> <li>Optional accessories</li> </ul>

# Ordering information

## Accessories

The following are the most important accessories available at the time this documentation was issued.

Listed accessories are technically compatible with the product in the instructions.

- **1.** Application-specific restrictions of the product combination are possible.
  - Ensure conformity of the measuring point to the application. This is the responsibility of the operator of the measuring point.
- 2. Pay attention to the information in the instructions for all products, particularly the technical data.
- 3. For accessories not listed here, please contact your Service or Sales Center.

Order no.	Bottle tray + bottles + cover
71111152	Bottle tray + 6 x 3 liter (0.79 US gal.) PE+ cover
71111154	Bottle tray + 12 x 1 liter (0.26 US gal.) PE + cover

Order no.	Distributor plate; centering plate
71111158	Distributor plate for 2 x 6 bottles
71111159	Distributor plate for 2 x 12 bottles

Order no.	Bottles + covers
71111164	1 liter (0.26 US gal.) PE + cover, 24 pcs
71111167	3 liter (0.79 US gal.) PE + cover, 12 pcs
71111169	13 liter (3.43 US gal.) PE + cover, 1 pc
71111172	30 liter (7.92 US gal.) PE + cover, 1 pc
71111173	60 liter (15.8 US gal.) PE + cover, 1 pc
71146645	17 liter (4.49 US gal.) PE, 1 pc

Order no.	Complete suction line
71111233	Suction line ID 10 mm (3/8"), PVC, reinforced fabric, length 10 m (33 ft), suction head V4A
71111234	Suction line ID 10 mm (3/8"), EPDM, length 10 m (33 ft), suction head V4A
71111235	Suction line ID 13 mm (1/2"), PVC, reinforced spiral wire, length 10 m (33 ft), suction head V4A
71111236	Suction line ID 13 mm (1/2"), EPDM, length 10 m (33 ft), suction head V4A

Order no.	Terminated hose: vacuum pump
71111188	Dosing hose to distributor, 2 pcs, material: silicon
71111189	Dosing hose to distributor, 25 pcs, material: silicon

Order no.	Terminated hose: peristaltic pump
71111191	Pump tubing, 2 pcs; material: silicon
71111192	Pump tubing, 25 pcs; material: silicon

Order no.	Retrofit kits
71111195	Kit CSF48: Retrofit kit distribution assembly (distribution arm, distribution arm drive)
71111196	Kit CSF48: Retrofit kit casters
71111197	Kit CSF48: Retrofit kit stand, V2A; 304(x)
71111198	Kit CSF48: Retrofit kit stand, V4A; 316(x)
71111199	Kit CSF48: Retrofit kit for flow assembly, without stand; with stand cover V2A; 304(x)
71136999	Kit CSF48: Retrofit kit service interface (CDI flange connector, counter nut)
71136101	Kit CSF48: Retrofit kit door stop (2x)

Order no.	Suction head
71111184	Suction head V4A for ID 10 mm (3/8"), 1 pc
71111185	Suction head V4A for ID 13 mm (1/2"), 1 pc

Order no.	Communication; software
71110815	SD card, 1 GB, Industrial Flash Drive
51516983	Commubox FXA291 + FieldCare Device Setup
71127100	SD card with Liquiline Firmware, 1 GB, Industrial Flash Drive



www.addresses.endress.com

