

Safety Instructions

Proline Promass 500

NEPSI: Zone 0/1
Zone 1
Zone 21



Proline Promass 500

Table of contents

Associated documentation	4
Certificates and declarations	5
Manufacturer address	5
Extended order code	5
Safety instructions: General	10
Safety instructions: Installation	12
Safety instructions: Zone 0	14
Safety instructions: Zone 21	14
Temperature tables	15
Explosion hazards arising from gas and dust	36
Connection values: Signal circuits	38

Associated documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

- *Device Viewer* (www.endress.com/deviceviewer): Enter serial number from nameplate.
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

To commission the device, please observe the Operating Instructions pertaining to the device:

Measuring device	Documentation code			
	HART	FOUNDATION Fieldbus	PROFIBUS PA	PROFIBUS DP
Promass A 500 (8A5B)	BA01526D	BA01559D	BA01548D	–
Promass A 500 (8A5C)	BA01817D	BA01883D	BA01869D	BA01870D
Promass E 500	BA01528D	BA01561D	BA01550D	BA01872D
Promass F 500	BA01529D	BA01562D	BA01551D	BA01873D
Promass H 500	BA01530D	BA01563D	BA01552D	BA01874D
Promass I 500	BA01531D	BA01564D	BA01553D	BA01875D
Promass O 500	BA01532D	BA01565D	BA01554D	BA01876D
Promass P 500	BA01533D	BA01566D	BA01555D	BA01877D
Promass Q 500	BA01534D	BA01567D	BA01556D	BA01878D
Promass S 500	BA01535D	BA01568D	BA01557D	BA01879D
Promass X 500	BA01536D	BA01569D	BA01558D	BA01880D

Measuring device	Documentation code		
	Modbus RS485	EtherNet/IP	PROFINET
Promass A 500 (8A5B)	BA01537D	BA01747D	BA01758D
Promass A 500 (8A5C)	BA01884D	BA01885D	BA01886D
Promass E 500	BA01539D	BA01749D	BA01760D
Promass F 500	BA01540D	BA01750D	BA01761D
Promass H 500	BA01541D	BA01751D	BA01762D
Promass I 500	BA01542D	BA01752D	BA01763D
Promass O 500	BA01543D	BA01753D	BA01764D
Promass P 500	BA01544D	BA01754D	BA01765D
Promass Q 500	BA01545D	BA01755D	BA01766D
Promass S 500	BA01546D	BA01756D	BA01767D
Promass X 500	BA01547D	BA01757D	BA01768D

Additional documentation

Contents	Document type	Documentation code
Explosion Protection	Brochure	CP00021Z/11
Ethernet-APL Installation Drawing	Installation Drawing	HE_01622

Please note the documentation associated with the device.

Certificates and declarations

NEPSI Declaration of Conformity

Certificate number:

GYJ22.1052X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- GB/T 3836.1-2021
- GB/T 3836.3-2021
- GB/T 3836.4-2021
- GB/T 3836.8-2021
- GB 3836.20-2010
- GB/T 3836.31-2021

Manufacturer address

Endress+Hauser Flowtec AG
 Kägenstrasse 7
 4153 Reinach BL
 Switzerland

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

$$\begin{array}{ccc}
 \text{*****} & - & \text{***** ... *****} & + & \text{A*B*C*D*E*F*G*...} \\
 \text{(Device type)} & & \text{(Basic specifications)} & & \text{(Optional specifications)}
 \end{array}$$

* = Placeholder
 At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Device type

The device and the device design is defined in the "Device type" section (Product root).

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications



The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Device type

Position	Order code for	Option selected	Description
1	Instrument family	8	Coriolis flowmeter
2	Sensor	A, E, F, H, I, O, P, Q, S, X ¹⁾	Sensor type
3	Transmitter	5	Transmitter type: 4-wire, remote version
4	Generation index	B, C	Platform generation
5, 6	Nominal diameter	Examples: 02, 04, 40, 50, 1H, 3E ²⁾ 3)	Nominal diameter of sensor

- 1) For replacement transmitter only: X
- 2) For the exact specification of the nominal diameter, see nameplate
- 3) For replacement transmitter only: XX

Proline 500 – digital	Proline 500
Order code for "Integrated ISEM Electronic", option A "Sensor"	Order code for "Integrated ISEM Electronic", option B "Transmitter"
 <p>1 Transmitter 2 Connecting cable 3 Sensor connection housing with integrated ISEM</p>	 <p>1 Transmitter with integrated ISEM 2 Connecting cable 3 Sensor connection housing</p>

Basic specifications

Position 1, 2 Order code for "Approval" Option selected	Position 10 Order code for "Integrated ISEM electronics" Option selected	Type of protection	
		Transmitter	Sensor
NA	B	Ex db eb ia [ia Ga] IIB T5...T6 Gb Ex tb [ia Da] IIIC T85°C Db	Ex ia IIB T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db
NB	B	Ex db eb ia [ia Ga] IIC T5...T6 Gb Ex tb [ia Da] IIIC T85°C Db	Ex ia IIC T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db
NC	B	Ex db ia [ia Ga] IIB T5...T6 Gb Ex tb [ia Da] IIIC T85°C Db	Ex ia IIB T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db
ND	B	Ex db ia [ia Ga] IIC T5...T6 Gb Ex tb [ia Da] IIIC T85°C Db	Ex ia IIC T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db
NI	A	[Ex ia] IIC [Ex ia] IIIC	Ex ia IIB T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db
NJ	A	[Ex ia] IIC [Ex ia] IIIC	Ex ia IIC T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db

Position 1, 2 Order code for "Approval" Option selected	Position 10 Order code for "Integrated ISEM electronics" Option selected	Type of protection	
		Transmitter	Sensor
NM	A	Ex ec nC [ia Ga] IIC T4...T5 Gc ²⁾ [Ex ia] IIIC	Ex ia IIB T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db
NN	A	Ex ec nC [ia Ga] IIC T4...T5 Gc ²⁾ [Ex ia] IIIC	Ex ia IIC T1...T6 Ga/Gb ¹⁾ Ex ia tb IIIC T** °C Db

- 1) Sensors Promass A DN 1, Promass H DN 8 to 50, Promass I DN 8 to 80 are only suitable for equipment protection level EPL Gb.
- 2) The marking changes with order code "Output; input 1", option HA, MC, RC or TA:
Ex ec nC [ic] [ia Ga] IIC T4...T5 Gc

Position	Order code for	Option selected	Description
4, 5	Output, input 1	BA	4-20mA HART
		CA	4-20mA Ex-i passive
		CC	4-20mA HART Ex-i active
		GA	PROFIBUS PA
		HA	PROFIBUS PA Ex-i
		LA	PROFIBUS DP
		MA	Modbus RS485
		MB	Modbus TCP with Ethernet-APL
		MC	Modbus TCP with Ethernet-APL Ex i
		NA	EtherNet/IP 2-port switch integrated
		RA	PROFINET IO 2-port switch integrated
		RB	PROFINET with Ethernet-APL
		RC	PROFINET with Ethernet-APL Ex i
		SA	FOUNDATION Fieldbus
TA	FOUNDATION Fieldbus Ex-i		
6	Output, input 2	A	W/o
		B	4-20mA
		C	4-20mA Ex-i passive
		D	Configurable I/O initial setting off
		E	Pulse/frequency/switch output
		F	Pulse output, phase-shifted
		G	Pulse/frequency/switch output Ex-i passive

Position	Order code for	Option selected	Description
		H	Relay
		I	4-20mA input
		J	Status input
7	Output, input 3	A	W/o
		B	4-20mA
		C	4-20mA Ex-i passive
		D	Configurable I/O initial setting off
		E	Pulse/frequency/switch output
		F	Pulse output, phase-shifted
		G	Pulse/frequency/switch output Ex-i passive
		H	Relay
		I	4-20mA input
		J	Status input
8	Output; input 4 ¹⁾	A	W/o
		B	4-20mA
		C	4-20mA Ex-i passive
		D	Configurable I/O initial setting off
		E	Pulse/frequency/switch output
		G	Pulse/frequency/switch output Ex-i passive
		H	Relay
		I	4-20mA input
		J	Status input
9	Display; Operation	F	4-line, illuminated; touch control
		G	4-line, illuminated; touch control + WLAN
10	Integrated ISEM Electronic	A	Sensor
		B	Transmitter
11	Transmitter Housing	A	Alu, coated
		D	Polycarbonate
		L	Cast, stainless
12	Sensor junction Housing	A	Alu, coated
		B	Stainless
		C	Ultra compact hygienic, stainless
		L	Cast, stainless

Position	Order code for	Option selected	Description
15, 16	Meas. Tube Mat., Wetted Parts Surface	LA	Stainl. steel, cryogenic -196°C/-320°F
21, 22	Device Model	A1	1
		A2	2

1) The order code "Output; input 4" is only available for the Proline 500 – digital transmitter.

Optional specifications

ID	Order code for	Option selected	Description
Jx	Test, certificate	JP	Ambient temperature -50 °C
Jx	Test, certificate	JQ	Ambient temperature, transmitter-50 °C Ambient temperature, sensor-60 °C
Px	Enclosed accessories	P8	Wireless antenna, wide area (external WLAN antenna) ¹⁾

1) The external WLAN antenna is available with the order code for "Accessory Enclosed", option P8.

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations or guidelines (e.g. GB/T 3836.15-2017)
- Install the device according to the manufacturer's instructions and the following standards:
 - GB 50257-2014 "Code for construction and acceptance of electric device for explosive atmospheres and fire hazard electrical equipment installation engineering"
 - GB/T 3836.13-2021 "Explosive atmospheres – Part 13: Equipment repair, overhaul, reclamation and modification"
 - GB/T 3836.15-2017 "Explosive atmospheres – Part 15: Electrical installations design, selection and erection"
 - GB/T 3836.16-2017 "Explosive atmospheres – Part 16: Electrical installations inspection and maintenance"
 - GB/T 3836.18-2017 "Explosive atmospheres – Part 18: Intrinsically safe electrical systems"
 - GB 15577-2018: "Safety regulations for dust explosion prevention and protection". (Only if installed in dust hazardous areas.)
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.

- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application, and the temperature classes.
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- When using in hybrid mixtures (gas and dust occurring simultaneously), observe additional measures for explosion protection.
- Open the housing cover of the transmitter housing in explosion protection Ex db only if one of the following conditions is met:
 - An explosive atmosphere is not present.
 - A waiting time of 10 minutes is observed after switching off the power supply.
The following warning notice is on the device:
WARNING – AFTER DE-ENERGIZING, DELAY 10 MINUTES
BEFORE OPENING ENCLOSURE IN TYPE OF PROTECTION EX D
- In devices with damaged Ex d threads:
 - Use in hazardous areas is not permitted.
 - Repair of Ex d threads is not permitted.
- Observe all the technical data of the device (see nameplate).
- Avoid electrostatic charge (e.g. caused by friction, cleaning, maintenance, strong currents in the medium):
On the attached stainless steel nameplate and on painted metallic housings that are not integrated into the local potential equalization system.

Safety instructions: Installation

- Continuous service temperature of the connecting cable:
-40 to +80 °C (-50 to +80 °C for optional specifications, ID Jx (Test, Certificate) = JP) (-60 to +80 °C for optional specifications, ID Jx (Test, Certificate) = JQ); in accordance with the range of service temperature taking into account additional influences of the process conditions ($T_{a,min}$ and $T_{a,max} + 20$ K).
- Only use certified cable entries suitable for the application. Observe selection criteria as per GB/T3836.15-2017.
- The following applies when connecting the transmitter with a connection compartment in Ex db:
Only use separately certified cables and wire entries (Ex db IIC) which are suitable for operating temperatures up to 85 °C and for IP 66/67. If using conduit entries, the associated sealing mechanisms must be mounted directly on the housing.
Plastic sealing plugs act as transport protection and have to be replaced by suitable, individually approved installation material. The mounted metal thread extensions and blind plugs are tested and certified as part of the housing for type of protection Ex db IIC. The thread extension or the blind plug labeled as follows for identification purposes:
 - Md: M20 x 1.5
 - d: NPT 1/2"
 - Gd: G 1/2"
- The following applies when connecting the transmitter with a connection compartment in Ex eb:
Only use separately certified cable and wire entries and sealing plugs (Ex eb IIC) which are suitable for operating temperatures up to 85 °C and for IP 66/67. The cables must be routed such that they are securely seated, and sufficient strain relief must be ensured. The mounted metal thread extensions and blind plugs supplied are tested and certified as part of the housing for type of protection Ex eb IIC. Plastic sealing plugs act as transport protection and have to be replaced by suitable, individually approved installation material. Supplied cable glands are separately certified and marked as components and meet device specification requirements.
- When the measuring device is connected, attention must be paid to explosion protection at the transmitter.

- In potentially explosive atmospheres:
 - Do not disconnect the electrical connection of the power supply circuit when energized.
 - Do not open the connection compartment cover when energized.
 - For measuring devices with order code "Approval", option NJ, NI the transmitter housing (plastic) is allowed to be installed at most in a Pollution Degree 2 environment.
 - Basic specification, order code for "Sensor connection housing", option B:
To protect the housing of stainless steel housings: Ensure that the housing gasket is flat and not bent when closing the housing cover. Replace bent gaskets.
 - When connecting through a conduit entry approved for this purpose, mount the associated sealing unit directly at the enclosure.
 - Seal unused entry glands with approved sealing plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
 - Only use certified sealing plugs. The metal sealing plugs supplied meet this requirement.
 - Transmitters with Ex db eb approval must not be connected via the service interface (CDI-RJ45)! Order code "Approval; Transmitter + Sensor", options (Ex de): NA, NB

Optional external WLAN antenna

- The external WLAN antenna can be used only in conjunction with an Ex eb or Ex ec connection compartment.
Order code for "Integrated ISEM Electronic", option B:
Use with an Ex db connection compartment is not permitted.
- Connect the antenna bushing H337 to the transmitter housing and tighten by hand.
- Use only external antennas supplied by Endress+Hauser.
- Connect antenna or antenna cable with plug-in connector type N (MIL-STD-348) to antenna bushing H337.

Optional RFID TAG

- In the case of high electromagnetic field intensities in accordance with GB/T 3836.15-2017: Use is not permitted.
- Avoid electrostatic charging.
- Ensure sufficient distance from processes generating high charges.

Intrinsic safety

- Observe the guidelines for interconnecting intrinsically safe circuits (e.g. GB/T 3836.15-2017 , Proof of Intrinsic Safety).
- When the intrinsically safe Ex ia circuits of the device are connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC or IIB, the type of protection changes to Ex ib IIC or Ex ib IIB.
- Proline 500 - digital (Order code for "Integrated ISEM electronics", option A)
The connecting cables between the transmitter and sensor must meet the following requirements:
 - Group IIC: $L/R \leq 0.0089 \text{ mH}/\Omega$ or $L_{\text{cable}} \leq 26 \text{ }\mu\text{H}$ and $C_{\text{cable}} \leq 760 \text{ nF}$
 - Group IIB: $L/R \leq 0.0356 \text{ mH}/\Omega$ or $L_{\text{cable}} \leq 104 \text{ }\mu\text{H}$ and $C_{\text{cable}} \leq 4.2 \text{ }\mu\text{F}$
- Proline 500 (Order code for "Integrated ISEM electronics", option B)
Connecting cables with a maximum length of 120 m must meet the following requirements:
 - Core/shield capacitance: maximum 0.5 pF/m
(Inductance: maximum 0.5 $\mu\text{H}/\text{m}$)
 - The connecting cables supplied meet this requirement.

Potential equalization

- Integrate the device into the potential equalization .
- If the ground connection has been established via the pipe as specified, it is also possible to integrate the sensor into the potential equalization system via the pipe.
- The antenna bushing H337 of the external antenna must be integrated into the potential equalization system. This is the case if the sensor is connected in accordance with the regulations via the coupling.

Safety instructions: Zone 0

For sensors with EPL Ga/Gb the zone 0 is permitted in the measuring tube.

Safety instructions: Zone 21

- To ensure dust-tightness, securely seal all housing openings, cable entries and sealing plugs.
- Only open all housing briefly, ensuring that no dust or moisture enters the housing.
- Cable routing shall be arranged so that the cables are not exposed to friction effects and static buildup due to the passage of dust. Precautions shall be taken to prevent the build-up of static an surfaces of cables.

Temperature tables

NOTICE

In case of heating, risk of overheating.

- ▶ On devices with Heating jacket the corresponding temperature tables for isolated sensor, are to be observed.
- ▶ Make sure that the heating medium, may not exceeded the maximum specified medium temperature of the exact used temperature classes of the device.

Ambient temperature

Minimum ambient temperature

- $T_a = -40\text{ °C}$ depending on the selected device variant (see nameplate)
- *Optional specification, ID Jx (Test, Certificate) = JP*
 $T_a = -50\text{ °C}$ depending on the selected device variant (see nameplate)
- Promass F, Q, X with order code "Integrated ISEM electronics", Option **B** and order code "Test, Certificate", Option **JQ**:
 - Sensor: -60 °C
 - Transmitter: -50 °C

Maximum ambient temperature

$T_a = +60\text{ °C}$ depending on the temperature class

Proline 500 – digital transmitter

Non-hazardous area, Zone 2

Transmitter housing material	$T_a\text{ [°C]}$			
	Non-hazardous area	T6	T5	T4
Aluminum	60	-	45	60
Polycarbonate	60	-	-	-

Proline 500 transmitter

Zone 1

$T_a\text{ [°C]}$	
T6	T5
55	60

Zone 21

Maximum surface temperature $T_a = 60\text{ °C}$	85 °C
--	-------

Medium temperature

Minimum medium temperature

- Promass A, F, H, I, P, Q, S, X:
 $T_m = -50\text{ °C}$
- Promass E, O:
 $T_m = -40\text{ °C}$
- Promass F, Q with cryogenic temperature version (order code for "Measuring tube material", option LA):
 $T_m = -196\text{ °C}$

Maximum medium temperature

- T_m for T1...T6 depending on the maximum ambient temperature T_a
- () = The maximum permitted medium temperatures in brackets only apply if the sensor is installed in such a way that the connection housing is not mounted above the sensor and free convection can occur on all sides.

Proline 500 – digital

Order code for "Integrated ISEM electronics", option A "Sensor"

Maximum medium temperature without thermal insulation according to Endress+Hauser specifications

*Promass A (8A5B**-*...)*

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	35	205	60	95	130	150	205	205
	50		-	95	130	150	205	205
	60		-	-	130	150	205	205

*Promass A (8A5C**-*...)*

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	35	205	55	85	130	150	205	205
	50		-	95	130	150	205	205
	55		-	-	130	150	205	205
	60		-	-	130	150	190	190

Promass E

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	35	150	40	60	130	130	150	150
	50		-	60	130	130	150	150
	60		-	-	130	130	150	150
80	35	150	40	60	110	150	150	150
	50		-	60	110	150	150	150
	60		-	-	110	150	150	150

Promass F

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08...50	35	150	40	65	130	150	150	150
	50		-	65	130	150	150	150
	60		-	-	130	130	130	130
	35	150 ²⁾	40	65	130	150	150	150
	50		-	65	130	150	150	150
	60		-	-	130	150	150	150
	35	240	40	65	130	160	240	240
	50		-	65	130	160	240	240
	60		-	-	130	160	240	240
15...25	35	350	40	80	130	175	275	350
	50		-	80	130	175	275	350
	60		-	-	130	175	240 (275)	240 (350)
80...250	35	150	40	65	110	150	150	150
	50		-	65	110	150	150	150
	60		-	-	110	130	130	130
	35	150 ²⁾	40	65	110	150	150	150
	50		-	65	110	150	150	150
	60		-	-	110	150	150	150
	35	240	40	65	110	170	240	240
	50		-	65	110	170	240	240
	60		-	-	110	170	240	240
50...250	35	350	40	80	120	175	275	350
	50		-	80	120	175	275	350
	60		-	-	120	175	240 (275)	240 (350)

- 1) Maximum temperature range, see nameplate
 2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass H

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	35	150	40	65	100	150	150	150
	50		-	65	100	150	150	150
	60		-	-	100	150	150	150
	35	205	40	65	100	160	205	205
	50		-	65	100	160	205	205
	60		-	-	100	160	205	205
15...50	35	150	40	65	115	150	150	150
	50		-	65	115	150	150	150
	60		-	-	115	150	150	150
	35	205	40	65	115	180	205	205
	50		-	65	115	180	205	205
	60		-	-	115	180	205	205

1) Maximum temperature range, see nameplate

Promass I

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...80	35	150	45	70	115	140	140	150
	50		-	70	115	140	140	150
	55		-	-	115	140	140	150
	60		-	-	115	140	140	140

Promass O

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80 ... 250	35	205	45	65	110	170	205	205
	50		-	65	110	170	205	205
	60		-	-	110	170	205	205

Promass P

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	35	150	45	65	100	150	150	150
	50		-	65	100	150	150	150
	60		-	-	100	150	150	150
	35	205	45	65	100	160	205	205
	50		-	65	100	160	205	205
	60		-	-	100	160	205	205
15...50	35	150	45	65	110	150	150	150
	50		-	65	110	150	150	150
	60		-	-	110	150	150	150
	35	205	45	65	110	180	205	205
	50		-	65	110	180	205	205
	60		-	-	110	180	205	205

1) Maximum temperature range, see nameplate

Promass Q

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25 ... 250	35	205	45	65	100	160	205	205
	50		-	65	100	160	205	205
	60		-	-	100	160	205	205
	35	150 ²⁾	45	65	100	150	150	150
	50		-	65	100	150	150	150
	60		-	-	100	150	150	150

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass S

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	35	150	45	65	100	150	150	150
	50		-	65	100	150	150	150
	60		-	-	100	150	150	150
15...50	35	150	45	65	110	150	150	150
	50		-	65	110	150	150	150
	60		-	-	110	150	150	150

Promass X

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	35	180	45	65	110	170	180	180
	50		-	65	110	170	180	180
	60		-	-	110	170	180	180

Maximum medium temperature with thermal insulation according to Endress+Hauser specifications



For information on the thermal insulation of the device, see the "Thermal insulation" section of the "Operating instructions" document.

Promass A (8A5B**-*..., 8A5C**-*...)

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	35	205	40	90	90	150	150	150
	40		-	90	90	150	150	150
	45		-	-	90	150	150	150
	50		-	-	90	120	120	120

Promass E

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	35	150	40	55	130	150	150	150
	50		-	55	130	150	150	150
80	35	150	40	55	110	150	150	150
	50		-	55	110	150	150	150

Promass F

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08...50	35	150	40	60	130	130	130	130
	45		-	60	130	130	130	130
	50		-	-	130	130	130	130
	35	150 ²⁾	40	60	130	150	150	150
	45		-	60	130	150	150	150
	50		-	-	130	150	150	150
	35	240	40	60	130	160	240	240
	45		-	60	130	160	240	240
	50		-	-	130	160	240	240

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
15...25	35	350	40	80	130	175	275	350
	50		-	80	130	175	275	350
	60		-	-	130	175	240 (275)	240 (350)
80...250	35	150	40	60	110	130	130	130
	45		-	60	110	130	130	130
	50		-	-	110	130	130	130
	35	150 ²⁾	40	60	110	150	150	150
	45		-	60	110	150	150	150
	50		-	-	110	150	150	150
	35	240	40	60	110	170	240	240
	45		-	60	110	170	240	240
	50		-	-	110	170	240	240
50...250	35	350	40	80	120	175	275	350
	50		-	80	120	175	275	350
	60		-	-	120	175	240 (275)	240 (350)

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass H

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	35	150	40	65	100	150	150	150
	45		-	65	100	150	150	150
	55		-	-	100	150	150	150
	35	205	40	65	100	160	205	205
	45		-	65	100	160	205	205
	55		-	-	100	160	205	205
15...50	35	150	40	65	115	150	150	150
	45		-	65	115	150	150	150
	55		-	-	115	150	150	150

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
	35	205	40	65	115	180	205	205
	45		-	65	115	180	205	205
	55		-	-	115	180	205	205

1) Maximum temperature range, see nameplate

Promass I

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...80	35	150	45	70	90	150	150	150
	45		-	70	90	150	150	150
	50		-	-	90	120	120	-

Promass O

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80...250	35	205	40	55	110	170	205	205
	50		-	55	110	170	205	205

Promass P

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	35	150	40	55	100	150	150	150
	45		-	55	100	150	150	150
	50		-	-	100	120	120	120
	35	205	40	55	100	160	205	205
	50		-	55	100	160	205	205
	55		-	-	100	160	205	205
15...50	35	150	40	55	110	150	150	150
	45		-	55	110	150	150	150

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
	50	205	-	-	110	120	120	120
	35		40	55	100	180	205	205
	50		-	55	100	180	205	205
	55		-	-	100	180	205	205

1) Maximum temperature range, see nameplate

Promass Q

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25...250	35	205	40	55	100	160	205	205
	50		-	55	100	160	205	205
25...250	35	150 ²⁾	40	55	100	150	150	150
	50		-	55	100	150	150	150

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass S

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	35	150	40	55	100	150	150	150
	45		-	55	100	150	150	150
	50		-	-	100	120	120	120
15...50	35	150	40	55	110	150	150	150
	45		-	55	110	150	150	150
	50		-	-	110	120	120	120


Promass X

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	35	180	40	55	120	170	180	180
	50		-	55	120	170	180	180
	55		-	-	120	170	180	180


With thermal insulation without Endress+Hauser specifications

The specified reference temperature T_{ref} and the maximum medium temperature $T_{m, max}$ for each temperature class must not be exceeded.

→  22



A0031199

 1 Position of reference point for temperature measurement

A Standard version

B Extended temperature version, cryogenic temperature version, high-temperature version

1 Reference point (T_{ref})

Reference temperature T_{ref}

T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
45	64	82	82	85	85

Proline 500

Order code for "Integrated ISEM electronics", option B "Transmitter"

Maximum medium temperature without thermal insulation according to Endress+Hauser specifications

*Promass A (8A5B**-*...)*

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	60	205	60	95	130	150	205	205

*Promass A (8A5C**-*...)*

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	55	205	55	95	130	150	205	205
	60		-	95	130	150	205	205

Promass E

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	50	150	50	100	130	130	150	150
	60		-	100	130	130	150	150
80	60	150	60	75	110	150	150	150

Promass F

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08...15	55	150	50	95	130	150	150	150
	60		-	95	130	150	150	150
	55	150 ²⁾	50	95	130	150	150	150
	60		-	95	130	150	150	150
	55	240	50	95	130	160	240	240
	60		-	95	130	160	240	240

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
15...25	60	350	70	95	130	175	265	350
25...40	55	150	55	95	130	150	150	150
	60		-	95	130	150	150	150
	55	150 ²⁾	55	95	130	150	150	150
	60		-	95	130	150	150	150
	55	240	55	95	130	160	240	240
	60		-	95	130	160	240	240
50	55	150	55	95	130	150	150	150
	60		-	95	130	150	150	150
	60	150 ²⁾	60	95	130	150	150	150
	60	240	60	95	130	170	240	240
80...250	55	150	55	75	110	150	150	150
	60		-	75	110	150	150	150
	60	150 ²⁾	60	75	110	150	150	150
	60	240	60	75	110	170	240	240
50...250	60	350	70	85	120	175	265	350

- 1) Maximum temperature range, see nameplate
 2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass H

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	50	150	50	65	100	150	150	150
	60		-	65	100	150	150	150
	50	205	50	65	100	160	205	205
	60		-	65	100	160	205	205
15...50	60	150	60	75	115	150	150	150
		205	60	75	115	180	205	205

- 1) Maximum temperature range, see nameplate

Promass I

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8, 15, 15FB, 25	60	150	60	95	130	150	150	150
25FB, 40, 40FB, 50, 50FB, 80	60	150	70	85	120	150	150	150
FB = Full bore								

Promass O

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80 ... 250	60	205	60	75	110	170	205	205

Promass P

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	45	150	45	65	100	150	150	150
	60		-	65	100	150	150	150
	45	205	45	65	100	160	205	205
	60		-	65	100	160	205	205
15...40	50	150	50	75	115	150	150	150
	60		-	75	115	150	150	150
	50	205	50	75	115	180	205	205
	60		-	75	115	180	205	205
50	60	150	60	75	115	150	150	150
		205	60	75	115	180	205	205

1) Maximum temperature range, see nameplate

Promass Q

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25 ... 250	60	205	55	75	110	160	205	205
		150 ²⁾	55	75	110	150	150	150

- 1) Maximum temperature range, see nameplate
 2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass S

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	45	150	45	65	100	150	150	150
	60		-	65	100	150	150	150
15...40	50		50	75	115	150	150	150
	60		-	75	115	150	150	150
50	60		60	75	115	150	150	150

Promass X

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	60	180	70	90	120	170	180	180

Maximum medium temperature with thermal insulation according to Endress+Hauser specifications



For information on the thermal insulation of the device, see the "Thermal insulation" section of the "Operating instructions" document.

Promass A (8A5B**-*...)

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	50	205	60	95	130	150	(180)	(180)
	60		60	95	130	150	150	150

Promass A (8A5C**-*...)

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
1...4	50	205	60	95	130	150	(180)	(180)
	55		55	95	130	150	150	150
	60		-	95	130	150	150	150

Promass E

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8...50	50	150	50	100	130	130	150	150
	60		-	100	130	130	150	150
80	60	150	60	75	110	150	150	150

Promass F

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
08...15	55	150	50	95	130	150	150	150
	60		-	95	130	150	150	150
	55	150 ²⁾	50	95	130	150	150	150
	60		-	95	130	150	150	150

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]						
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]	
	55	240	50	95	130	160	240	240	
	60		-	95	130	160	240	240	
15...25	60	350	70	95	130	175	265	350	
25...40	55	150	55	95	130	150	150	150	
	60		-	95	130	150	150	150	
	55	150 ²⁾	55	95	130	150	150	150	
	60		-	95	130	150	150	150	
	55		240	55	95	130	160	240	240
	60			-	95	130	160	240	240
50	55	150	55	95	130	150	150	150	
	60		-	95	130	150	150	150	
	60	150 ²⁾	60	95	130	150	150	150	
	60	240	60	95	130	170	240	240	
80...250	55	150	55	75	110	150	150	150	
	60		-	75	110	150	150	150	
	60	150 ²⁾	60	95	130	150	150	150	
	60	240	60	75	110	170	240	240	
50...250	60	350	70	85	120	175	265	350	

- 1) Maximum temperature range, see nameplate
 2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass H

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	50	150	50	65	100	150	150	150
	60		-	65	100	150	150	150
	50	205	50	65	100	160	205	205
	60		-	65	100	160	205	205
15...50	60	150	60	75	115	150	150	150
		205	60	75	115	180	205	205

- 1) Maximum temperature range, see nameplate

Promass I

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8, 15, 15FB, 25	60	150	60	95	130	150	150	150
25FB, 40, 40FB, 50, 50FB, 80			70	85	120	150	150	150
FB = Full bore								

Promass O

DN	T _a [°C]	T _{m,max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
80...250	60	205	60	75	110	170	205	205

Promass P

DN	T _a [°C]	T _{m,max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	45	150	45	65	100	150	150	150
	60		-	65	100	150	150	150
	45	205	45	65	100	160	205	205
	60		-	65	100	160	205	205
15...40	50	150	50	75	115	150	150	150
	60		-	75	115	150	150	150
	50	205	50	75	115	180	205	205
	60		-	75	115	180	205	205
50	60	150	60	75	115	150	150	150
	60	205	60	75	115	180	205	205

1) Maximum temperature range, see nameplate

Promass Q

DN	T _a [°C]	T _{m, max} ¹⁾ [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
25...250	60	205	55	75	110	160	205	205
		150 ²⁾	55	75	110	150	150	150

- 1) Maximum temperature range, see nameplate
 2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass S

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
8	45	150	45	65	100	150	150	150
	60		-	65	100	150	150	150
15...40	50	150	50	75	115	150	150	150
	60		-	75	115	150	150	150
50	60	150	60	75	115	150	150	150


Promass X

DN	T _a [°C]	T _{m, max} [°C]	T _m [°C]					
			T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
350	60	180	70	90	120	170	180	180

With thermal insulation without Endress+Hauser specifications

The specified reference temperature T_{ref} and the maximum medium temperature $T_{m,max}$ for each temperature class must not be exceeded.

→  32



A0031199

 2 Position of reference point for temperature measurement

- A Standard version
 B Extended temperature version, cryogenic temperature version, high-temperature version
 1 Reference point (T_{ref})

Reference temperature T_{ref}

T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
63	72	84	91	91	91

Explosion hazards arising from gas and dust

Determining the temperature class and surface temperature with the temperature table

- In the case of gas: Determine the temperature class as a function of the maximum ambient temperature T_a and the maximum medium temperature T_m .
- In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature T_a and the maximum medium temperature T_m .

Connection values: Signal circuits

The following tables contain specifications which are dependent on the transmitter type and its input and output assignment. Compare the following specifications with those on the nameplate of the transmitter.

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

FOUNDATION Fieldbus

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	26 (A)	27 (B)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

PROFIBUS DP

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

PROFIBUS PA

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

Modbus RS485

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

Modbus TCP with Ethernet-APL

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

EtherNet/IP

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	EtherNet/IP (RJ45 connector)		24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

PROFINET

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	PROFINET (RJ45 connector)		24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

PROFINET with Ethernet-APL

Supply voltage		Input/output 1		Input/output 2		Input/output 3		Input/output 4	
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Device-specific terminal assignment: adhesive label in terminal cover.									

Safety-related values

Order code for "Output; input 1"	Output type	Safety-related values "Output; input 1"	
		26 (+)	27 (-)
Option BA	Current output 4 to 20 mA HART	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	
Option GA	PROFIBUS PA	$U_N = 32 V_{DC}$ $U_M = 250 V_{AC}$	
Option LA	PROFIBUS DP	$U_N = 32 V_{DC}$ $U_M = 250 V_{AC}$	
Option MA	Modbus RS485	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	

Order code for "Output; input 1"	Output type	Safety-related values "Output; input 1"	
		26 (+)	27 (-)
Option MB	Modbus TCP with Ethernet-APL	APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	
Option SA	FOUNDATION Fieldbus	$U_N = 32 V_{DC}$ $U_M = 250 V_{AC}$	
Option NA	EtherNet/IP	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	
Option RA	PROFINET	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	
Option RB	PROFINET with Ethernet-APL	APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$	

Order code for "Output; input 2"; "Output; input 3"; "Output; input 4"	Output type	Safety-related values					
		Output; input 2		Output; input 3		Output; input 4 ¹⁾	
		24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Option B	Current output 4 to 20 mA	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$					
Option D	User-configurable input/output	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$					
Option E	Pulse/frequency/switch output	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$					
Option F	Double pulse output	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$					
Option H	Relay output	$U_N = 30 V_{DC}$ $I_N = 100 mA_{DC}/500 mA_{AC}$ $U_M = 250 V_{AC}$					
Option I	Current input 4 to 20 mA	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$					
Option J	Status input	$U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$					

1) The order code "Output; input 4" is only available for the Proline 500 – digital transmitter.

Intrinsically safe values

Order code for "Output; input 1"	Output type	Intrinsically safe values "Output; input 1"	
		26 (+)	27 (-)
Option CA	Current output 4-20mA HART Ex-i passive	$U_i = 30 \text{ V}$ $I_i = 100 \text{ mA}$ $P_i = 1.25 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$	
Option CC	Current output 4-20mA HART Ex-i active	Ex ia ¹⁾ $U_0 = 21.8 \text{ V}$ $I_0 = 90 \text{ mA}$ $P_0 = 491 \text{ mW}$ $L_0 = 4.1 \text{ mH(IIC)}/$ 15 mH(IIB) $C_0 = 160 \text{ nF(IIC)}/$ 1160 nF(IIB) $U_i = 30 \text{ V}$ $I_i = 10 \text{ mA}$ $P_i = 0.3 \text{ W}$ $L_i = 5 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$	Ex ic ²⁾ $U_0 = 21.8 \text{ V}$ $I_0 = 90 \text{ mA}$ $P_i = 491 \text{ mW}$ $L_0 = 9 \text{ mH(IIC)}/$ 39 mH(IIB) $C_0 = 600 \text{ nF(IIC)}/$ 4000 nF(IIB)
Option HA	PROFIBUS PA Ex i (STANDARD + FISCO)	Ex ia ¹⁾ $U_i = 30 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8.5 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$	Ex ic ²⁾ $U_i = 32 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8.5 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$

Order code for "Output; input 1"	Output type	Intrinsically safe values "Output; input 1"	
		26 (+)	27 (-)
Option MC	Modbus TCP with Ethernet-APL Ex i	2-WISE power load, APL port profile SLAA³⁾ Ex ia $U_i = 17,5 \text{ V}$ $I_i = 380 \text{ mA}$ $P_i = 5,32 \text{ W}$ $L_i = 10 \mu\text{H}$ $C_i = 5 \text{ nF}$ Cable specifications according to 2-WISE: $R_c = 15 \text{ to } 150 \Omega/\text{km}$ $L_c = 0.4 \text{ to } 1 \text{ mH}/\text{km}$ $C_c = 45 \text{ to } 200 \text{ nF}/\text{km}$ $C_c = C_c \text{ line}/\text{line} + 0,5 C_c \text{ line}/\text{screen}$, if both lines are floating, or $C_c = C_c \text{ line}/\text{line} + C_c \text{ line}/\text{screen}$, if the screen is connected to one line Length of cable (not including cable stubs): $\leq 200 \text{ m}$ (656.2) Length of cable stubs: $\leq 1 \text{ m}$ (3.3 ft)	
Option RC	PROFINET with Ethernet-APL Ex i		
Option TA	FOUNDATION Fieldbus Ex i (STANDARD + FISCO)	Ex ia¹⁾ $U_i = 30 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8,5 \text{ W}$ $L_i = 10 \mu\text{H}$ $C_i = 5 \text{ nF}$	Ex ic²⁾ $U_i = 32 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8,5 \text{ W}$ $L_i = 10 \mu\text{H}$ $C_i = 5 \text{ nF}$

- 1) Only for the order code for "Approval", option NA, NB, NC, ND
- 2) Only for the order code for "Approval", option NB, ND
- 3) For further options see Ethernet-APL Installation Drawing HE_01622.

Order code for "Output; input 2"; "Output; input 3"; "Output; input 4"	Output type	Intrinsically safe values					
		Output; input 2		Output; input 3		Output; input 4 ¹⁾	
		24 (+)	25 (-)	22 (+)	23 (-)	20 (+)	21 (-)
Option C	Current output 4 to 20 mA Ex i passive	$U_i = 30 \text{ V}$ $I_i = 100 \text{ mA}$ $P_i = 1.25 \text{ W}$ $L_i = 0$ $C_i = 0$					
Option G	Pulse/frequency/switch output Ex i passive	$U_i = 30 \text{ V}$ $I_i = 100 \text{ mA}$ $P_i = 1.25 \text{ W}$ $L_i = 0$ $C_i = 0$					

- 1) The order code "Output; input 4" is only available for the Proline 500 – digital transmitter.



71596204

www.addresses.endress.com
