## Technical Information Cerabar S PMC71, PMP71, PMP75

Process pressure measurement

## Pressure transmitter with ceramic and metallic measuring cells

#### Applications

The device is used for the following measuring tasks:

- Absolute pressure and gauge pressure measurement in gases, steams or liquids in all areas of process engineering and process measurement technology
- Level, volume or mass measurements in liquids
- High process temperatures
  - up to 150 °C (302 °F) without diaphragm seal
  - up to 400 °C (752 °F)with typical diaphragm seals
- High pressures up to 700 bar (10500 psi)
- Low-energy version with voltage output (1-5V DC), e.g. for operation on solaroperated control units (Remote Terminal Unit (RTU))

#### Your benefits

- Very good reproducibility and long-term stability
- High reference accuracy up to ±0.025 %
- Turn down up to 100:1, higher on request
- Used for process pressure monitoring up to SIL 3, certified to IEC 61508 by TÜV SÜD
- High level of safety during operation thanks to function monitoring from the measuring cell to the electronics
- Easy electronics replacement guaranteed with HistoROM®/M-DAT





## Table of contents

About this document	6 6
Function and system design         Device features         Measuring principle         Product design         Applications suitable for custody transfer measurement         Communication protocol	8 10 12 12 12
Input	<b>13</b> 13 13
Output Output signal . Signal range . Signal on alarm . Load . Damping . Alarm current . Firmware version . Protocol-specific data HART . Wireless HART data . Protocol-specific data PROFIBUS PA . Protocol-specific data FOUNDATION Fieldbus .	16 16 16 17 18 18 18 18 18 19 19 20
Power supply . Terminal assignment . Supply voltage . Current consumption . Electrical connection . Terminals . Cable entries . Device plugs . Cable specification . Start-up current . Residual ripple . Overvoltage protection (optionally for HART, PROFIBUS PA and FOUNDATION Fieldbus) . Influence of power supply .	<ul> <li>23</li> <li>24</li> <li>25</li> <li>25</li> <li>25</li> <li>26</li> <li>27</li> <li>28</li> <li>28</li> <li>28</li> <li>28</li> </ul>
Performance characteristics for measuring devices with ceramic process membrane	29 29 29 31 31 31 32 33

Performance characteristics for measuring	
devices with metal process membrane	34
Response time	34
Reference operating conditions	34
Total performance	34
Resolution	37
Total error	37
Long-term stability	38
Response time T63 and T90	38
Installation factors	40
Installation	41
General installation instructions	41
Measuring arrangement for devices without diaphragm	
seals – PMC71, PMP71	41
Measuring arrangement for devices with diaphragm seals	
– PMP75	41
Orientation	41
Wall and pipe mounting, transmitter (optional)	42
Wall and pipe mounting, valve manifold (optional)	42
Heat insulation – PMC71 high-temperature version	42
Mounting of PVDF screw-in fittings	43
"Separate housing" version	44
Turning the housing	45
Environment	46
Ambient temperature range	46
Storage temperature range	47
Degree of protection	47
Climate class	47
Electromagnetic compatibility	47
Vibration resistance	47
Oxygen applications	48
PWIS-free applications	48
Ultrapure gas applications	48
Hydrogen applications	48 48
Operation in very corrosive environment	48
Process	49
Process temperature limits	49
Process temperature limits of capillary armoring: PMP75	50
Pressure specifications	51
Mechanical construction	52
Device height	52
T14 housing, optional display on the side	53
T17 housing (hygienic), optional display on the side	54
PMC71: height H	54
Process connections for PMC71 with internal process	
membrane	56
Process connections for PMC71 with internal process	
membrane	58
Process connections for PMC71 with flush membrane	59
Process connections for PMC71 with flush membrane	60
Process connections for PMC71 with flush membrane	61
Process connections for PMC71 with flush membrane	64
PMC71 hygiene	65

Process connections for PMP71 with internal process	
membrane	67
Process connections for PMP71 with internal process	
membrane	68
Process connections for PMP71 with internal process	
membrane	69
Process connections for PMP71 with flush membrane	70
Process connections for PMP71 with flush membrane	72
Process connections for PMP71 with flush membrane	73
Process connections for PMP71 with flush membrane	74
Process connections for PMP71 with flush-mounted	
process isolating diaphragm	75
PMP71: process connections with flush-mounted process	
isolating diaphragm	76
Process connections for PMP71	77
Process connections for PMP71	77
Valve manifold DA63M- (optional)	78
PMP75 basic device	79
Process connections for PMP75 with flush membrane	80
Process connections for PMP75 with flush membrane	82
PMP75: Process connections with flush TempC	
membrane	83
Process connections for PMP75 with flush-mounted	
process isolating diaphragm	84
Process connections for PMP75 with flush-mounted	
process isolating diaphragm	85
Hygienic process connections for PMP75 with flush mount	
process isolating diaphragm	86
Hygienic process connections for PMP75 with flush-	
mounted process isolating diaphragm	87
Hygienic process connections for PMP75 with flush	
membrane	89
Process connections for PMP75 with flush membrane	92
Process connections for PMP75 with flush membrane	95
Process connections for PMP75	99
Separate housing: Wall and pipe mounting with mounting	
bracket	.03
Flushing rings	.04
	.04
$\mathbf{r}$	.05
F	.08
Fill fluid	.10

Operability	111
Operating concept	111
Local operation	111
Remote operation	
HistoROM <sup>®</sup> /M-DAT (optional)	116
System integration	

#### Planning instructions for diaphragm seal

systems	117
Applications	117
Design and mode of operation	118
Diaphragm seal filling oils	120
Cleaning instructions	120
Installation instructions	120
Vacuum applications	125
Certificates and approvals	126
CE mark	126
RoHS	126

RCM-Tick marking ..... 126

Ex approvals	126
EAC conformity	126
Suitable for hygiene applications	126
Certificate of current Good Manufacturing Practices	
(cGMP)	126
Functional safety SIL/ IEC 61508 Declaration of	
Conformity (optional)	126
Overfill prevention	126
CRN approval	127
Other standards and quidelines	127
Pressure Equipment Directive 2014/68/EU (PED)	127
Manufacturer declarations	127
Marine approval	128
	128
Drinking water approval	120
Approvals for custody transfer	_
MID Parts Certificate	128
Classification of process sealing between electrical	
systems and (flammable or combustible) process fluids in	4.0.0
accordance with ANSI/ISA 12.27.01	129
Inspection certificate	129
Calibration	130
Service	130
Ordering information	131
Special device versions	131
Scope of delivery	131
Measuring point (TAG)	131
Configuration data sheet	132
Accessories	134
HistoROM <sup>®</sup> /M-DAT	134
Welding flanges and weld-in adapters	134
Manifolds	134
Additional mechanical accessories	134
Service-specific accessories	134
	105
Supplementary documentation	135
Field of Activities	135
Technical Information	135
Special Documentation	135
Operating Instructions	135
Brief Operating Instructions	135
Functional safety manual (SIL)	135
Overfill prevention	135
Safety Instructions (XA)	135
Installation/Control Drawings	137

### About this document

**Document function** 

The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.

#### Symbols used

#### Safety symbols

Symbol	Meaning
<b>A</b> DANGER	<b>DANGER!</b> This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.
	<b>WARNING!</b> This symbol alerts you to a dangerous situation. Failure to avoid this situation may result in serious or fatal injury.
	<b>CAUTION!</b> This symbol alerts you to a dangerous situation. Failure to avoid this situation may result in minor or moderate injury.
NOTICE	<b>NOTE!</b> This symbol contains information on procedures and other circumstances that do not result in personal injury.

#### **Electrical symbols**

Symbol	Meaning	Symbol	Meaning
	<b>Protective ground connection</b> A terminal that must be connected to ground prior to establishing any other connections.	4	<b>Ground connection</b> A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.

#### Symbols for certain types of Information

Symbol	Meaning
$\checkmark$	Permitted Procedures, processes or actions that are permitted.
	<b>Preferred</b> Procedures, processes or actions that are preferred.
	<b>Forbidden</b> Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
	Reference to documentation
	Reference to page
	Reference to graphic
	Visual inspection

#### Symbols in graphics

Symbol	Meaning
1, 2, 3	Item numbers
1. , 2. , 3	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections

#### Documentation


See the "Supplementary documentation" section  $\rightarrow$  🗎 135



The document types listed are available: In the Download Area of the Endress+Hauser Internet site: www.endress.com → Download


#### Safety Instructions (XA)

See the "Safety instructions" section  $\rightarrow$  🗎 135




Item	Term/abbreviation	Explanation
1	OPL	The OPL (overpressure limit) for the measuring device depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to the measuring cell. Also observe pressure-temperature dependency. For the relevant standards and additional information, see the "Pressure specifications" section $\rightarrow \textcircled{B} 51$ . The OPL may only be applied for a limited period of time.
2	MWP	The MWP (maximum working pressure) for the sensors depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to the measuring cell. Also observe pressure-temperature dependency. For the relevant standards and additional information, see the "Pressure specifications" section $\rightarrow \cong 51$ . The maximum working pressure may be applied at the device for an unlimited period. The maximum working pressure can also be found on the nameplate.
3	Maximum sensor measuring range	Span between LRL and URL This sensor measuring range is equivalent to the maximum calibratable/adjustable span.
4	Calibrated/adjusted span	Span between LRV and URV Factory setting: 0 to URL Other calibrated spans can be ordered as customized spans.
р	-	Pressure
-	LRL	Lower range limit
-	URL	Upper range limit
-	LRV	Lower range value
-	URV	Upper range value
-	TD (turn down)	Turn down Example - see the following section.

#### Turn down calculation



- Calibrated/adjusted span Zero point-based span URL sensor 1
- 2 3



#### Registered trademarks

Registered trademark of the FieldComm Group, Austin, USA

#### **PROFIBUS®**


Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

#### **FOUNDATION**<sup>TM</sup>**Fieldbus**

Registered trademark of the FieldComm Group, Austin, Texas, USA

### Function and system design

#### **Device features**



#### Field of application

- Gauge pressure and absolute pressure
- Level

#### Process connections

PMC71:

- Thread
- EN flanges DN 25 DN 80
- ANSI flanges 1" 4"
- JIS flanges 50 A 100 A

PMP71:

- Thread
- DN 25 DN 80
- ASME 1 ½" 4"
- JIS 25 A 100 A
- Oval flange adapters
- Prepared for diaphragm seal mount

PMP75:

Wide range of diaphragm seals

#### Measuring ranges

- PMC71: From -100/0 to 100 mbar (-1.5/0 to 1.5 psi) to -1/0 to 40 bar (-15/0 to 600 psi)
- PMP71: From -400/0 to 400 mbar (-6/0 to 6 psi) to -1/0 to 700 bar (-15/0 to 10500 psi)
- PMP75: From -400/0 to 400 mbar (-6/0 to 6 psi) to -1/0 to 400 bar (-15/0 to 6000 psi)

#### OPL

- PMC71: max. 60 bar (900 psi)
- PMP71: max. 1050 bar (15750 psi)
- PMP75: max. 600 bar (9000 psi)

#### Process temperature range (temperature at process connection)

- PMC71:-25 to +125 °C (-13 to +257 °F)
  - -20 to  $+150\ ^\circ C$  (–4 to  $+302\ ^\circ F)$  (High-temperature version, see Product Configurator "Additional option 1" or 110 "Additional option 2" section, option "T")
- PMP71:-40 to +125 °C (-40 to +257 °F)
- PMP75: -70 to +400 °C (-94 to +752 °F) (depending on the filling oil)

#### Ambient temperature range

- Without LCD display: up to -60 to +85 °C (-76 to +185 °F)
- With LCD display: -20 to +70 °C (-4 to +158 °F) (extended temperature application range -60 to +85 °C (-76 to +185 °F) with limitations in optical properties, such as display speed and contrast)
- Separate housing:  $-20 \text{ to } +60 \degree \text{C} (-4 \text{ to } +140 \degree \text{F})$
- PMP75: Diaphragm seal systems depending on the version

#### **Reference** accuracy

- PMC71: Up to  $\pm 0.05\%$  of the set span
- PLATINUM version: up to  $\pm 0.025$  % of the set span
- PMP71: Up to ±0.05% of the set span
- PLATINUM version: up to  $\pm 0.025$  % of the set span
- PMP75: Up to ±0.075% of the set span

#### Supply voltage

Supply voltage non-Ex

- 4 to 20 mA HART: 10.5 to 45 V DC
- 1-5V DC: 9 to 35 V DC
- PROFIBUS PA and FOUNDATION Fieldbus: 9 to 32 V DC

Supply voltage Ex ia 10.5 to 30 V DC

10.5 to 50 v DC

Supply voltage Ex d (1-5V DC) 9 to 35 V DC

#### Output

- 4 to 20 mA with superimposed HART protocol
- 1-5V DC
- PROFIBUS PA
- FOUNDATION Fieldbus

#### Options


- Inspection certificate 3.1
- HistoROM<sup>®</sup>/M-DAT memory chip
- Separate housing
- PMP75: gold-coated process isolating diaphragm
- PMP71, PMP75: gold-rhodium coated process isolating diaphragm
- PMP71, PMP75:NACE-compliant materials

#### Specialties

- PMC71:
  - Metal-free measurement with PVDF connection
  - Special cleaning of the transmitter to remove paint-wetting substances, for use in paint shops
- PMP71:
  - Process connections with minimum oil volume
  - Gas-tight, elastomer-free
- PMP75:
  - Wide range of diaphragm seals
  - For high medium temperatures
  - Process connections with minimum oil volume
  - Completely welded versions

#### Measuring principle

#### Devices with ceramic process isolating diaphragm (Ceraphire®)




- 1 Air pressure (gauge pressure sensors)
- 2 Ceramic substrate
- 3 Electrodes
- 4 Ceramic process isolating diaphragm

The ceramic sensor is an oil-free sensor, i.e. the process pressure acts directly on the robust ceramic process isolating diaphragm and causes it to deflect. A pressure-dependent change in capacitance is measured at the electrodes of the ceramic substrate and the process isolating diaphragm. The measuring range is determined by the thickness of the ceramic process isolating diaphragm.

#### Advantages:

- Guaranteed overload resistance up to 40 times the nominal pressure (see "OPL" column in table)  $\rightarrow \cong 13$ )
- The ultrapure 99.9% ceramic (Ceraphire<sup>®</sup>, see also "www.endress.com/ceraphire") ensures:
  - Extremely high chemical durability
  - High mechanical durability
- Suitable for vacuums
- Secondary containment for enhanced integrity
- Process temperatures up to 150 °C (302 °F)

#### Devices with metallic process isolating diaphragm



- 1 Silicon measuring element, substrate
- 2 Wheatstone bridge
- 3 Channel with fill fluid
- 4 Metal process isolating diaphragm

#### PMP71

The process pressure deflects the metal process isolating diaphragm of the sensor and a fill fluid transfers the pressure to a Wheatstone bridge (semiconductor technology). The pressure-dependent change in the bridge output voltage is measured and evaluated.

#### Advantages:

- Can be used for process pressures up to 700 bar (10500 psi)
- High long-term stability
- Guaranteed overload resistance up to 4 times the nominal pressure
- Secondary containment for enhanced integrity
- Significantly reduced thermal effect e.g. compared to diaphragm seal systems with capillaries

#### PMP75

The operating pressure acts on the process isolating diaphragm of the diaphragm seal and is transferred to the process isolating diaphragm of the sensor by a diaphragm seal fill fluid. The process isolating diaphragm is deflected and a fill fluid transfers the pressure to a resistance measuring bridge. The pressure-dependent change in the bridge output voltage is measured and evaluated.

#### Advantages:

- Depending on the version, can be used for process pressures up to 400 bar (6000 psi) and for extreme process temperatures
- High long-term stability
- Guaranteed overload resistance up to 4 times the nominal pressure
- Secondary containment for enhanced integrity

Product design	Level measurement (level, volume and mass):	
	$h = \frac{p}{\rho \cdot g}$	
	h Height (level) p Pressure ρ Density of the medium g Gravitation constant	
	<ul> <li>Your benefits</li> <li>Selection of the level operating mode which is optimum for your application in the device software</li> <li>Volume and mass measurements in any vessel shape by means of a freely programmable characteristic curve</li> <li>Choice of diverse level units with automatic unit conversion</li> <li>A customized unit can be specified.</li> <li>Has a wide range of uses, e.g.</li> <li>for foam formation</li> <li>in vessels with agitators of screen fittings</li> <li>for liquid gases</li> </ul>	
Applications suitable for custody transfer measurement	<ul> <li>The Parts Certificate is issued on the basis of the following standards:</li> <li>WELMEC guide 8.8 "General and Administrative Aspects of the Voluntary System of Modular Evaluation of Measuring instruments under the MID".</li> <li>OIML R117-1 Edition 2007 (E) "Dynamic measuring systems for liquids other than water".</li> <li>EN 12405-1/A1 Edition 2006 "Gas meters - Conversion devices - Part 1: Volume conversion".</li> </ul>	
Communication protocol	<ul> <li>4 to 20 mA with HART communication protocol</li> <li>PROFIBUS PA</li> <li>Endress+Hauser devices meet the requirements specified by the FISCO model.</li> <li>Due to a low current consumption of 13 mA ± 1 mA, the following number of devices can be operated on one bus segment if installing as per FISCO: up to 7 devices for Ex ia, CSA IS and FM IS applications or up to 27 devices for all other applications e.g. in non-hazardous areas, Ex nA etc. Further information on PROFIBUS PA can be found in Operating Instructions BA00034S "PROFIBUS DP/PA: Guidelines for planning and commissioning" and in the PNO Guideline.</li> <li>FOUNDATION Fieldbus</li> <li>Endress+Hauser devices meet the requirements specified by the FISCO model.</li> <li>Due to a low current consumption of 15.5 mA ± 1 mA, the following number of devices can be operated on one bus segment if installing as per FISCO: up to 6 devices for Ex ia, CSA IS and FM IS applications or up to 24 devices for all other applications e.g. in non-hazardous areas, Ex nA etc. Further information on FOUNDATION Fieldbus, such as requirements for bus system components, can be found in Operating Instructions BA00013S "FOUNDATION Fieldbus Overview".</li> </ul>	

## Input

Measured variable

#### Measured process variables

- Absolute pressure
- Gauge pressure

Measuring range

#### PMC71 – with ceramic process isolating diaphragm (Ceraphire®) for gauge pressure

Sensor	Maximum sensor measuring range		Lowest	MWP	OPL	Vacuum resistance	Option <sup>2)</sup>
	lower (LRL)	upper (URL)	calibratable span <sup>1)</sup>				
	[bar (psi)]	[bar (psi)]	[bar (psi)]	[bar (psi)]	[bar (psi)]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	-
100 mbar (1.5 psi)	-0.1 (-1.5)	+0.1 (+1.5)	0.005 (0.075)	2.7 (40.5)	4 (60)	0.7 (10.5)	1C
250 mbar (3.75 psi)	-0.25 (-3.75)	+0.25 (+3.75)	0.005 (0.075)	3.3 (49.5)	5 (75)	0.5 (7.5)	1E
400 mbar (6 psi)	-0.4 (-6)	+0.4 (+6)	0.005 (0.075)	5.3 (79.5)	8 (120)	0	1F
1 bar (15 psi)	-1 (-15)	+1 (+15)	0.01 (0.15)	6.7 (100.5)	10 (150)	0	1H
2 bar (30 psi)	-1 (-15)	+2 (+30)	0.02 (0.3)	12 (180)	18 (270)	0	1K
4 bar (60 psi)	-1 (-15)	+4 (+60)	0.04 (0.6)	16.7 (250.5)	25 (375)	0	1M
10 bar (150 psi)	-1 (-15)	+10 (+150)	0.1 (1.5)	26.7 (400.5)	40 (600)	0	1P
40 bar (600 psi)	-1 (-15)	+40 (+600)	0.4 (6)	40 (600)	60 (900)	0	1S

1) Turndown > 100:1 on request or can be set on device

2) Product Configurator, order code for "Sensor range; sensor over pressure limit"

PMC71 – with ceramic process isolating diaphragm (Ceraphire <sup>®</sup> ) for al	absolute pressure
---	-------------------

Sensor	Maximum sensor measuring range			MWP	OPL	Vacuum resistance	Option <sup>2)</sup>
	lower (LRL)	upper (URL)	calibratable span <sup>1)</sup>				
	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar (psi)]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	
100 mbar (1.5 psi)	0	+0.1 (+1.5)	0.005 (0.075)	2.7 (40.5)	4 (60)	0	2C
250 mbar (3.75 psi)	0	+0.25 (+3.75)	0.005 (0.075)	3.3 (49.5)	5 (75)	0	2E
400 mbar (6 psi)	0	+0.4 (+6)	0.005 (0.075)	5.3 (79.5)	8 (120)	0	2F
1 bar (15 psi)	0	+1 (+15)	0.01 (0.15)	6.7 (100.5)	10 (150)	0	2H
2 bar (30 psi)	0	+2 (+30)	0.02 (0.3)	12 (180)	18 (270)	0	2K
4 bar (60 psi)	0	+4 (+60)	0.04 (0.6)	16.7 (250.5)	25 (375)	0	2M
10 bar (150 psi)	0	+10 (+150)	0.1 (1.5)	26.7 (400.5)	40 (600)	0	2P
40 bar (600 psi)	0	+40 (+600)	0.4 (6)	40 (600)	60 (900)	0	2S

1) Turndown > 100:1 on request or can be set on device

2) Product Configurator, order code for "Sensor range; sensor over pressure limit"

Sensor	Maximum sensor measuring range		Lowest	MWP	OPL	Vacuum resistance <sup>2)</sup>	Option <sup>3)</sup>
	lower (LRL)	upper (URL)	calibratable span <sup>1)</sup>			Silicone oil/ Inert oil	
	[bar (psi)]	[bar (psi)]	[bar (psi)]	[bar (psi)]	[bar (psi)]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	
400 mbar (6 psi)	-0.4 (-6)	+0.4 (+6)	0.005 (0.075)	4 (60)	6 (90)		1F
1 bar (15 psi)	-1 (-15)	+1 (+15)	0.01 (0.15)	6.7 (100)	10 (150)		1H
2 bar (30 psi)	-1 (-15)	+2 (+30)	0.02 (0.3)	13.3 (200)	20 (300)	-	1K
4 bar (60 psi)	-1 (-15)	+4 (+60)	0.04 (0.6)	18.7 (280.5)	28 (420)		1M
10 bar (150 psi)	-1 (-15)	+10 (+150)	0.1 (1.5)	26.7 (400.5)	40 (600)	0.01/0.04 (0.15/0.6)	1P
40 bar (600 psi)	-1 (-15)	+40 (+600)	0.4 (6)	100 (1500)	160 (2400)		1S
100 bar (1500 psi)	-1 (-15)	+100 (+1500)	1.0 (15)	100 (1500)	400 (6000) 4)	-	1U
400 bar (6000 psi)	-1 (-15)	+400 (+6000)	4.0 (60)	400 (6000)	600 (9000)		1W
700 bar (10 500 psi) <sup>5)</sup>	-1 (-15)	+700 (+10500)	7.0 (105)	700 (10500)	1050 (15750)		1X

1) Turn down > 100:1 on request or can be set on device

2) The vacuum resistance applies for the measuring cell under reference operating conditions. A ceramic process isolating diaphragm is recommended for applications in the limit range. For type PMP75, the pressure and temperature application limits of the selected filling oil must also be observed → 
<sup>(B)</sup> 120.

3) Product Configurator, order code for "Sensor range; sensor over pressure limit"

4) If the option "IN" is ordered in the order code for "Test, certificate", then the OPL is 160 bar (2 400 psi).

5) PMP71 only, PMP75 on request

Sensor	Maximum sensor measuring range <sup>1)</sup>			MWP	OPL	Vacuum resistance <sup>3)</sup>	Option <sup>4)</sup>
	lower (LRL)	upper (URL)	calibratable span <sup>2)</sup>			Silicone oil/ Inert oil	
	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar (psi)]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	
400 mbar (6 psi)	0	+0.4 (+6)	0.005 (0.075)	4 (60)	6 (90)		2F
1 bar (15 psi)	0	+1 (+15)	0.01 (0.15)	6.7 (100)	10 (150)	-	2H
2 bar (30 psi)	0	+2 (+30)	0.02 (0.3)	13.3 (200)	20 (300)	-	2K
4 bar (60 psi)	0	+4 (+60)	0.04 (0.6)	18.7 (280.5)	28 (420)	-	2M
10 bar (150 psi)	0	+10 (+150)	0.1 (1.5)	26.7 (400.5)	40 (600)	0.01/0.04 (0.15/0.6)	2P
40 bar (600 psi)	0	+40 (+600)	0.4 (6)	100 (1500)	160 (2400)		2S
100 bar (1500 psi)	0	+100 (+1500)	1.0 (15)	100 (1500)	400 (6000) <sup>5)</sup>	-	2U
400 bar (6000 psi)	0	+400 (+6000)	4.0 (60)	400 (6000)	600 (9000)		2W
700 bar (10 500 psi) <sup>6)</sup>	0	+700 (+10500)	7.0 (105)	700 (10500)	1050 (15750)		2X

1) PMP75: Within the sensor measuring range, the minimum upper range value of 80 mbar<sub>abs</sub> (1.16 psi<sub>abs</sub>) must be observed.

2) Turn down > 100:1 on request or can be set on device

3) The vacuum resistance applies for the measuring cell under reference operating conditions. A ceramic process isolating diaphragm is recommended for applications in the limit range. For type PMP75, the pressure and temperature application limits of the selected filling oil must also be observed → 
<sup>(B)</sup> 120.

4) Product Configurator, order code for "Sensor range; sensor over pressure limit"

5) If the option "JN" is ordered in the order code for "Test, certificate", then the OPL is 160 bar (2 400 psi).

6) PMP71 only, PMP75 on request

Sensor	Maximum se measuring r		Min. WP for gas applications suitable	Min. WP for liquid applications suitable	MWP	OPL	Vacuum resistance <sup>1)</sup>	Option <sup>2)</sup>
	lower (LRL) <sup>3)</sup>	upper (URL) <sup>4)</sup>	for custody transfer measurement	for custody transfer measurement			Silicone oil/ Inert oil	
[bar (psi)]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar (psi)]	[bar (psi)]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar <sub>abs</sub> (psi <sub>abs</sub> )]	[bar (psi)]	
10 (150)	0	+10 (150)	0.5 (7.5)	0.5 (7.5)	26.7 (400.5)	40 (600)	0.01/0.04 (0.15/1)	MP
50 (750)	0	+50 (750)	10 (150)	2.5 (37.5)	100 (1500)	400 (6000)	0.01/0.04 (0.15/1)	MT
100 (1500)	0	+100 (1500)	5 (75)	5 (75)	100 (1500)	400 (6000)	0.01/0.04 (0.15/1)	MU

#### PMP71 - metallic process isolating diaphragms for absolute pressure with MID parts certificate

The vacuum resistance applies to the measuring cell under reference operating conditions Product Configurator, order code for "Sensor range; sensor over pressure limit" 1)

2)

3) By default, the device is set to a lower sensor measuring range of 0 bar. Please specify when ordering if the lower sensor measuring range is to be set to a different default value.

4) Max. WP (working pressure) for gas and liquid applications suitable for calibration to regulatory standards

0

R

Dutput signal	<ul> <li>4 to 20 mA with superimposed digital communication protocol HART, 2-wire</li> <li>1-5V DC, 3-wire</li> <li>Digital communication signal PROFIBUS PA (Profile 3.0), 2-wire</li> <li>Signal coding: Manchester Bus Powered (MBP): Manchester II</li> <li>Transmission rate: 31.25 KBit/s voltage mode</li> <li>Digital communication signal FOUNDATION Fieldbus, 2-wire</li> <li>Signal coding: Manchester Bus Powered (MBP): Manchester II</li> <li>Transmission rate: 31.25 KBit/s voltage mode</li> </ul>					
Output	Internal + LCD External + LCD Internal					
			A0021280			
		Option <sup>1)</sup>				
4 to 20mA HART	В	А	С			
4 to 20mA HART, Li=0	E	D	F			
1-5V DC	Н	G	-			

М

Р

1) Product Configurator, order code for "Display, operation: "

PROFIBUS PA

FOUNDATION Fieldbus

Signal range	4 to 20 mA				
	3.8 mA to 20.5 mA				
	1-5V DC				
	0.95 to 5.125 V				
Signal on alarm	4 to 20 mA HART				
	As per NAMUR NE43.				
	<ul> <li>Max. alarm: can be set from 21 to 23 mA (factory setting: 22 mA)</li> <li>Hold measured value: last measured value is held</li> <li>Min. alarm: 3.6 mA</li> </ul>				
	1-5V DC				
	<ul> <li>Max. alarm: can be set from 5.25 to 5.75 V</li> <li>Min. Alarm: 0.9 V</li> </ul>				
	PROFIBUS PA				
	As per NAMUR NE43.				
	Can be set in the Analog Input Block.				
	Options: Last Valid Out Value (factory setting)     Fail Safe Value				

Status bad

#### FOUNDATION Fieldbus

Ν

Q

As per NAMUR NE43.

Can be set in the Analog Input Block.

## Output

Output signal


Options:

- Last Good Value
- Fail Safe Value (factory setting)
- Wrong Value

Load

#### 4 to 20 mA HART

In order to guarantee sufficient terminal voltage in two-wire devices, a maximum load resistance R (including line resistance) must not be exceeded depending on the supply voltage  $U_0$  of the supply unit. In the following load diagrams, observe the position of the jumper and the explosion protection:



A Jumper for 4 to 20 mA test signal set to "Non-test" position

*B* Jumper for 4 to 20 mA test signal set to "Test" position

1 Power supply 10.5 (11.5) to 30 V DC for 1/2 G, 1 GD, 1/2 GD, FM IS, CSA IS, IECEx ia, NEPSI Ex ia

2 Power supply 10.5 (11.5) to 45 V DC for devices for non-hazardous areas, 1/2 D, 1/3 D, 2 G Ex d, 3 G Ex nA, FM XP, FM DIP, FM NI, CSA XP, CSA dust ignition-proof, NEPSI Ex d

- 3 Power supply 11 (12) to 45 V DC for PMC71, Ex d[ia], NEPSI Ex d[ia]
- 4 R<sub>Lmax</sub> maximum load resistance
- U Supply voltage



When operating via a handheld terminal or via a PC with an operating program, a minimum communication resistor of 250  $\Omega$  must be taken into account.

#### 1-5V DC

The load must be at least  $100 \text{ k}\Omega$ .

Damping	<ul> <li>A damping affects all outputs (output signal, display):</li> <li>via local display, handheld terminal or PC (handheld terminal operating program, continuous from 0 to 999 s</li> <li>Also for HART and PROFIBUS PA: Via DIP switch on the elect switch position "on" = set value and "off"</li> <li>1-5V DC: via DIP switch on electronic insert switch position "on" = set value and "off"</li> <li>Factory setting: 2 s</li> </ul>	
Alarm current	Designation	Option <sup>1)</sup>
	Min alarm current	J
	HART burst mode PV	J
	Min alarm current + HART burst mode PV	J
	1) Product Configurator, order code for "Additional options 1" and "	Additional options 2"
Firmware version	Designation	Option <sup>1)</sup>
	02.20.zz, HART 7, DevRev22	72
	02.11.zz, HART 5, DevRev21	73

02.20.zz, HART 7, DevRev22	72
02.11.zz, HART 5, DevRev21	73
04.00.zz, FF, DevRev07	74
04.01.zz, PROFIBUS PA, DevRev03	75
02.10.zz, HART 5, DevRev21	76
03.00.zz, FF, DevRev06	77
04.00.zz, PROFIBUS PA	78
02.30.zz, HART 7	71

1) Product Configurator, order code for "Firmware version"

Protocol-specific data HART	Manufacturer ID	17 (11 hex)
	Device type ID	24 (18 hex)
	Device revision	<ul> <li>21 (15 hex) - SW version 02.1y.zz - HART specification 5</li> <li>22 (16 hex) - SW version 02.2y.zz - HART specification 7</li> </ul>
	HART specification	• 5 • 7
	DD revision	<ul> <li>4 (Russian in language selection) for device revision 21</li> <li>3 (Dutch in language selection) for device revision 21</li> <li>1 for device revision 22</li> </ul>
	Device description files (DTM, DD)	Information and files under:
		<ul><li>www.endress.com</li><li>www.fieldcommgroup.org</li></ul>
	HART load	Min. 250 Ω

HART device variables	The measured values are assigned to the device variables as follows:	
	Measured values for PV (primary variable) <ul> <li>Pressure</li> <li>Level</li> <li>Tank content</li> </ul>	
	Measured values for SV, TV (second and third variable) Pressure	
	Measured values for QV (fourth variable) Temperature	
Supported functions	<ul> <li>Burst mode</li> <li>Additional transmitter status</li> <li>Device locking</li> <li>Alternative measuring modes</li> </ul>	

#### Wireless HART data

Protocol-specific data PROFIBUS PA

Minimum starting voltage	11.5 V (default) or 10.5 V if jumper not set to "Test" position $^{1)}$
Start-up current	12 mA
Starting time	10 s
Minimum operating voltage	11.5 V (default) or 10.5 V if jumper not set to "Test" position $^{1)}$
Multidrop current	4 mA
Time for connection setup	1 s

1) Or higher if operating near the ambient temperature limits (–40 to +85  $^{\circ}$ C (–40 to +185))

Manufacturer ID	17 (11 hex)
Identification number	1541 hex
Profile version	3.0 • SW version 03.00.zz • SW version 04.00.zz
	3.02 SW version 04.01.zz ( device revision 3) Compatibility with SW version 03.00.zz and higher.
GSD revision	<ul><li>4 (SW version 3.00.zz and 4.00.zz)</li><li>5 (device revision 3)</li></ul>
DD revision	<ul><li>1 (SW version 3.00.zz and 4.00.zz)</li><li>1 (device revision 3)</li></ul>
GSD file	Information and files under:
DD files	<ul><li>www.endress.com</li><li>www.profibus.org</li></ul>
Output values	Measured values for PV (via Analog Input Function Block)  Pressure Level Tank content
	Measured values for SV <ul> <li>Pressure</li> <li>Temperature</li> </ul>

Input values	Input value sent from PLC, can be shown on display	
Supported functions	<ul> <li>Identification &amp; maintenance, simplest device identifier on the control system and nameplate</li> <li>Condensed status (only with Profile Version 3.02)</li> <li>Automatic ID number adjustment and switchable to the following ID numbers (only with Profile Version 3.02):</li> <li>9700: Profile-specific transmitter identification number with the "Classic" or "Condensed" status.</li> <li>1501: Compatibility mode for the old Cerabar S generation (PMC731, PMP731, PMC631, PMP635).</li> <li>1541: Identification number of the new Cerabar S generation (PMC71, PMP71, PMP75).</li> <li>Device locking: The device can be locked by hardware or software.</li> </ul>	

#### Protocol-specific data FOUNDATION Fieldbus

Manufacturer ID	452B48 hex
Device type	1007 hex
Device revision	<ul> <li>6 - SW version 03.00.zz</li> <li>7 - SW version 04.00.zz (FF-912)</li> </ul>
DD revision	<ul><li> 3 (device revision 6)</li><li> 2 (device revision 7)</li></ul>
CFF revision	<ul><li> 4 (device revision 6)</li><li> 1 (device revision 7)</li></ul>
DD files	Information and files under:
CFF files	<ul><li>www.endress.com</li><li>www.fieldcommgroup.org</li></ul>
Device tester version (ITK version)	<ul><li> 5.0 (device revision 6)</li><li> 6.01 (device revision 7)</li></ul>
Number of ITK test campaign	<ul><li>IT054600 (Device Revision 6)</li><li>IT085500 (Device Revision 7)</li></ul>
Link-Master (LAS) capable	Yes
Choice of "Link Master" and "Basic Device"	Yes; Factory setting: Basic Device
Node address	Factory setting: 247 (F7 hex)
Supported functions	Field diagnostics profile (only with FF912)
	The following methods are supported: Reboot Configure error as warning or alarm HistoROM Peakhold Alarm info Sensor trim
Number of VCRs	<ul><li> 44 (device revision 6)</li><li> 24 (device revision 7)</li></ul>
Number of Link Objects in VFD	50

#### Virtual communication references (VCRs)

	Device revision 6	Device revision 7
Permanent Entries	44	1
Client VCRs	0	0
Server VCRs	5	10
Source VCRs	8	43
Sink VCRs	0	0
Subscriber VCRs	12	43
Publisher VCRs	19	43

#### Link settings

	Device revision 6	Device revision 7
Slot time	4	4
Min. Inter PDU delay	12	10
Max. response delay	10	10

#### **Transducer Blocks**

Block	Contents	Output values
TRD1 Block	Contains all parameters related to the measurement	<ul><li>Pressure or level (channel 1)</li><li>Process temperature (channel 2)</li></ul>
Service Block	Contains service information	<ul> <li>Pressure after damping (channel 3)</li> <li>Pressure peakhold indicator (channel 4)</li> <li>Counter for max. pressure transgressions (channel 5)</li> </ul>
Diagnostic block	Contains diagnostic information	Error code via DI channels (channel 0 to 16)
Display block	Contains parameters to configure the onsite display	No output values

#### Function blocks

Block	Contents	Number	Execution time		Functionality	
		Blocks	Device Revision 6	Device Revision 7	Device Revision 6	Device Revision 7
Resource Block	The Resource Block contains all the data that uniquely identify the device. It is an electronic version of a nameplate of the device.	1			enhanced	enhanced
Analog Input Block 1 Analog Input Block 2	The AI Block receives the measuring data from the Sensor Block, (selectable via a channel number) and makes the data available to other function blocks at its output. Enhancement: Digital outputs for process alarms, fail safe mode	2	45 ms	45 ms (without trend and alarm reports)	enhanced	enhanced
Digital Input Block	This block contains the discrete data of the Diagnose Block (selectable via a channel number 0 to 16) and provides them for other blocks at the output.	1	40 ms	30 ms	standard	enhanced
Digital Output Block	This block converts the discrete input and thus initiates an action (selectable via a channel number) in the DP Flow Block or in the Service Block. Channel 1 resets the counter for max. pressure transgressions.	1	60 ms	40 ms	standard	enhanced
PID Block	This block is used as a proportional-integral-derivative controller and can be used universally for closed-loop-control in the field. It enables cascade mode and feedforward control. Input IN can be indicated on the display. The selection is performed in the Display Block (DISPLAY_MAIN_LINE_CONTENT).	1	120 ms	70 ms	standard	enhanced
Arithmetic Block	This block is designed to permit simple use of popular measurement math functions. The user does not have to know how to write equations. The math algorithm is selected by name, chosen by the user for the function to be performed.	1	50 ms	40 ms	standard	enhanced
Input Selector Block	The Input Selector Block facilitates the selection of up to four inputs and generates an output based on the configured action. This block normally receives its inputs from AI Blocks. The block enables the selection of maximum, minimum, average and 'first good' values. Inputs IN1 to IN4 can be shown on the display. The selection is performed in the Display Block (DISPLAY_MAIN_LINE_CONTENT).	1	35 ms	35 ms	standard	enhanced
Signal Characterizer Block	The Signal Characterizer Block has two sections, each with an output value that is a non-linear function of the input value. The non-linear function is generated by a single look-up table with 21 arbitrary x-y pairs.	1	30 ms	40 ms	standard	enhanced
Integrator Block	The Integrator Block integrates a variable as a function of the time or accumulates the counts from a Pulse Input Block. The block may be used as a totalizer that counts up until reset or as a batch totalizer that has a setpoint, where the integrated or accumulated value is compared to pre-trip and trip settings, generating a binary signal when the setpoint is reached.	1	35 ms	40 ms	standard	enhanced
Analog Alarm Block	This block contains all process alarm conditions (working like a comparator) and represents them at the output.	1	35 ms	35 ms	standard	enhanced

Additional function block information:

Instantiate Function Block	JA	JA
Number of additional instantiatable function blocks	11	5

### Power supply


#### **WARNING**

Electrical safety is compromised by an incorrect connection!

- When using the measuring device in hazardous areas, installation must also comply with the corresponding national standards and regulations and the Safety Instructions or Installation or Control Drawings → 
  <sup>(1)</sup>
  <sup>(2)</sup>
  <sup>(2)</sup>
  <sup>(2)</sup>
  <sup>(2)</sup>
  <sup>(3)</sup>
  <sup>(3)</sup>
- Devices with integrated overvoltage protection must be grounded  $\rightarrow \square$  28.
- Protective circuits against reverse polarity, HF influences and overvoltage peaks are integrated.


#### Terminal assignment

#### 4 to 20 mA HART




- 1 Housing
- 2 Supply voltage
- 3 4 to 20 mA
- 4 Devices with integrated overvoltage protection are labeled "OVP" (overvoltage protection) here.
- 5 External ground terminal
- 6 4 to 20 mA test signal between positive and test terminal
- 7 Internal ground terminal
- 8 Jumper for 4 to 20 mA test signal  $\rightarrow \cong 24$

#### 1-5V DC



- 1 Housing
- 2 Supply voltage
- 3 1-5V DC
- 4 Overvoltage protection (OVP) marking
- 5 External ground terminal
- 6 Terminals
- 7 Internal ground terminal

#### **PROFIBUS PA and FOUNDATION Fieldbus**



- 1 Housing
- 2
- Supply voltage Devices with integrated overvoltage protection are labeled "OVP" (overvoltage protection) here. External ground terminal 3
- 4
- 5 Internal ground terminal

#### Supply voltage

#### 4 to 20 mA HART

Electronic version	Jumper for 4 to 20 mA test signal in "Test" position (delivery status)	Jumper for 4 to 20 mA test signal in "Non-test" position
Version for non-hazardous area	11.5 to 45 V DC	10.5 to 45 V DC
Intrinsically safe	11.5 to 30 V DC	10.5 to 30 V DC
<ul><li>Other types of protection</li><li>Devices without a certificate</li></ul>	11.5 to 45 V DC (Versions with 35 V DC plug-in connector)	10.5 to 45 V DC (Versions with 35 V DC plug-in connector)

#### Measuring a 4 to 20 mA test signal

Jumper position for test signal	Description
Test ✓	<ul> <li>Measurement of 4 to 20 mA test signal via the positive and test terminal: possible. (Thus, the output current can be measured without interruption via the diode.)</li> <li>As-delivered state</li> <li>Minimum supply voltage: 11.5 V DC</li> </ul>
	<ul> <li>Measurement of 4 to 20 mA test signal via the positive and test terminal: not possible.</li> <li>Minimum supply voltage: 10.5 V DC</li> </ul>

#### 1-5V DC

- Non-hazardous area: 9 to 35 V DC
- Ex-d: 9 to 35 V DC

	PROFIBUS PA			
	<ul> <li>Version for non-hazardous areas: 9 to 32 V DC</li> </ul>			
	<ul> <li>Ex ia:</li> <li>Installation in bus system according to FISCO model: Ui=17.5 V DC</li> <li>Point-to-point installation: Ui = 24 V DC</li> </ul>			
	FOUNDATION Fieldbus			
	<ul> <li>Version for non-hazardous areas: 9 to</li> <li>Ex ia: <ul> <li>Installation in bus system according</li> <li>Point-to-point installation: Ui = 24</li> </ul> </li> </ul>	g to FISCO model: Ui=17.5	5 V DC	
Current consumption	<ul> <li>1-5V DC:</li> <li>9 V = 1.8 mA</li> <li>35 V = 0.8 mA</li> <li>PROFIBUS PA: 13 mA ±1 mA, switch</li> <li>FOUNDATION Fieldbus: 15.5 mA ±1</li> <li>21</li> </ul>			
Electrical connection	PROFIBUS PA			
	The digital communication signal is trar provides the power supply. For further i further bus system components such as Instructions BA00034S "PROFIBUS DP/I Guideline.	nformation on the netwo bus cables, see the releva	rk structure and grounding and for nt documentation, e.g. Operating	
	FOUNDATION Fieldbus			
	The digital communication signal is tran provides the power supply. For further i further bus system components such as Instructions BA00013S "FOUNDATION	nformation on the netwo bus cables, see the releva	rk structure and grounding and for nt documentation, e.g. Operating	
Terminals	<ul> <li>Supply voltage and internal ground te</li> <li>External ground terminal: 0.5 to 4 mm</li> </ul>	erminal: 0.5 to 2.5 mm <sup>2</sup> (2 m <sup>2</sup> (20 to 12 AWG)	20 to 14 AWG)	
Cable entries	Approval	Cable gland	Clamping range	
	Standard, II 1/2 G Ex ia, IS	Plastic M20x1.5	5 to 10 mm (0.2 to 0.39 in)	
	ATEX II 1/2 D, II 1/3 D, II 1/2 GD Ex ia, II 1 GD Ex ia, II 3 G Ex nA	Metal M20x1.5 (Ex e)	7 to 10.5 mm (0.28 to 0.41 in)	


#### 1-5V DC

The cable entries have a 1/2 FNPT thread. The connection on the customer's side is protected by a plastic connector. A cable gland is not envisaged.

For additional technical data, see section on housing  $\rightarrow \implies 53$ 

#### Device plugs


#### Connection for devices with Harting plug Han7D



- A Electrical connection for devices with Harting plug Han7D
- *B* View of plug-in connection on the device
- Brown
- $\pm$  Green/yellow
- + Blue


Material: CuZn, gold-plated plug-in jack and plug contacts

#### Connection of cable version




- 1 rd = red
- $2 \quad bk = black$
- 3 gnye = green
- 4 4 to 20 mA

#### Connection of cable version 1-5V DC



- 1 rd = red
- $2 \quad bk = black$
- 3 gnye = green
- 4 1-5V DC

#### Connection of devices with M12 plug



- 1 Signal +
- 2 Not assigned
- 3 Signal –
- 4 Ground

Endress+Hauser offers the following accessories for devices with an M12 plug:

Plug-in jack M 12x1, straight

- Material: body PA; union nut CuZn, nickel-plated
- Degree of protection (fully locked): IP67
- Order number: 52006263


Plug-in jack M 12x1, elbowed

- Material: body PBT/PA; union nut GD-Zn, nickel-plated
- Degree of protection (fully locked): IP67
- Order number: 71114212

Cable 4x0.34 mm<sup>2</sup> (20 AWG) with M12 elbowed socket, screw plug, length 5 m (16 ft)

- Material: body PUR; union nut CuSn/Ni; cable PVC
- Degree of protection (fully locked): IP67
- Order number: 52010285

#### Connection of devices with 7/8" plug



- 1 Signal -
- 2 Signal +
- 3 Shield
- 4 Not assigned

Male thread: 7/8 - 16 UNC

Material: 316L (1.4401)

Degree of protection: IP68

#### Cable specification

#### HART

- Endress+Hauser recommends using shielded, twisted-pair two-wire cables.
- Cable outer diameter: 5 to 9 mm (0.2 to 0.35 in) depending on the cable entry used  $\rightarrow \cong 25$

#### 1-5V DC

- Endress+Hauser recommends using a shielded cable.
- Cable outer diameter: 5 to 9 mm (0.2 to 0.35 in) depending on the cable entry used  $\rightarrow \cong 25$

#### Maximum cable length

The following table shows the tolerance of the voltage output for a representative cable with a length of up to 100 m (328 ft), a resistance of 18 Ohm/km and specification 18 AWG (cable cross-section  $0.8 \text{ mm}^2$ ).

Tolerance of voltage output at cable end	Length
0.5 mV	25 m (82 ft)
1 mV	50 m (164 ft)
1.5 mV	75 m (246 ft)
2 mV	100 m (328 ft)

#### PROFIBUS PA

Use a twisted, shielded twin-core cable, preferably cable type A.



For further information on the cable specifications, see Operating Instructions BA00034S "PROFIBUS DP/PA: Guidelines for planning and commissioning", the PNO Guideline 2.092 PROFIBUS PA User and Installation Guideline" and IEC 61158-2 (MBP).

#### FOUNDATION Fieldbus

Use a twisted, shielded twin-core cable, preferably cable type A.

For further information on the cable specifications, see Operating Instructions BA00013S "FOUNDATION Fieldbus Overview", FOUNDATION Fieldbus Guideline and IEC 61158-2 (MBP).

Start-up current	12 mA
Residual ripple	Without influence on 4 to 20 mA signal up to $\pm$ 5% residual ripple within the permitted voltage range [according to HART hardware specification HCF_SPEC-54 (DIN IEC 60381-1)].
Overvoltage protection (optionally for HART, PROFIBUS PA and FOUNDATION Fieldbus)	<ul> <li>Overvoltage protection:</li> <li>Nominal functioning DC voltage: 600 V</li> <li>Nominal discharge current: 10 kA</li> <li>Surge current check î = 20 kA satisfied as per DIN EN 60079-14: 8/20 μs</li> <li>Arrester AC current check I = 10 A satisfied</li> </ul>
	Ordering information: Product Configurator, order code for "Additional options 1" or Additional options 2", option "M"
	NOTICE Device could be destroyed! ► Devices with integrated overvoltage protection must be grounded.
Influence of power supply	≤0.0006 % of URL/1 V

## Performance characteristics for measuring devices with ceramic process membrane

Response time	HART			
	<ul> <li>Acyclic: min. 330 ms, typically 590 ms (depending on command # and number of preambles)</li> <li>Cyclic (burst): min. 160 ms, typically 350 ms (depending on command # and number of preambles)</li> </ul>			
	PROFIBUS PA			
	<ul> <li>Acyclic: approx. 60 ms to 70 ms (depending on Min. Slave Interval)</li> <li>Cyclic: approx. 10 ms to 13 ms (depending on Min. Slave Interval)</li> </ul>			
	FOUNDATION Fieldbus			
	<ul> <li>Acyclic: typically 100 ms (for standard bus parameter settings)</li> <li>Cyclic: max. 20 ms (for standard bus parameter settings)</li> </ul>			
Reference operating conditions	• As per IEC 62828-2 / IEC 60770 • Ambient temperature $T_A$ = constant, in the range +22 to +28 °C (+72 to +82 °F) • Humidity $\varphi$ = constant, in the range: 5 to 80 % RH ± 5 % • Ambient pressure $p_U$ = constant, in the range:860 to 1060 mbar (12.47 to 15.37 psi) • Position of the measuring cell: horizontal ±1° • Input of LOW SENSOR TRIM and HIGH SENSOR TRIM for lower range value and upper range value • Span based on zero point • Membrane material PMC71: Al <sub>2</sub> O <sub>3</sub> aluminum oxide ceramic FDA, ultrapure 99.9 % • Supply voltage: 24 V DC ±3 V DC • Load with HART: 250 $\Omega$ • Turn down (TD) = URL/   URV - LRV			
Total performance	The performance characteristics refer to the accuracy of the device. The factors that influence the accuracy can be divided into two groups <ul> <li>Total performance of device</li> <li>Installation factors</li> </ul>			
	All of the performance characteristics meet the requirement of $\ge \pm 3$ sigma.			
	The total performance of the device comprises the reference accuracy and the ambient temperature effect and is calculated using the following formula:			
	Total performance = $\pm \sqrt{((E1)^2 + (E2)^2)}$			
	E1 = Reference accuracy			
	E2 = Temperature effect			
	Calculation of E2:			
	Temperature effect per $\pm 28$ °C (50 °F)			
	(Corresponds to a range of $-3$ to $+53$ °C (+27 to $+127$ °F))			
	$E2 = E2_{M} + E2_{E}$			
	$E2_{M} = Main$ temperature error			
	$E2_E = Electronics error$			
	The values refer to the calibrated span.			

#### Calculation of the total performance with the Endress+Hauser Applicator

Detailed inaccuracies, e.g. for other temperature ranges or the high-temperature version of the device can be calculated with the Applicator "Sizing Pressure Performance".



#### Reference accuracy [E1]

Reference accuracy comprises the non-linearity [IEC 62828-1/DIN EN 61298-2] including the hysteresis [IEC 62828-1/DIN EN 61298-2] and the non-repeatability [IEC 62828-1/DIN EN 61298-2] in accordance with the limit point method as per [IEC 62828-1/DIN EN 60770-2]. Reference accuracy for standard up to TD 100:1, for platinum up to TD 5:1.

#### 100 mbar (1.5 psi) sensor

- Standard:  $TD \le 10:1 = \pm 0.075$  %;  $TD > 10:1 = \pm 0.0075$  % · TD
- Platinum: TD 1:1 = ±0.05 %; TD > 1:1 = ±0.075 %

250 mbar (3.75 psi) sensor

- Standard: TD ≤ 10:1 = ±0.075 %; TD > 10:1 = ±0.0075 % · TD
- Platinum: TD  $\geq$  1:1 = ±0.05 %

400 mbar (6 psi) and 1 bar (15 psi) sensor

- Standard:  $\overline{\text{TD}} \le 10:1 = \pm 0.05$  %;  $\overline{\text{TD}} > 10:1 = \pm 0.005$  %  $\cdot$   $\overline{\text{TD}}$
- Platinum:  $TD \ge 1:1 = \pm 0.035 \%$

2 bar (30 psi) sensor

- Standard: TD  $\leq$  10:1 = ±0.05 %; TD > 10:1 = ±0.005 % · TD
- Platinum: TD 1:1 = ±0.025 %; TD ≥ 1:1 = ±0.035 %

4 bar (60 psi) sensor

- Standard:  $TD \le 10:1 = \pm 0.05$  %;  $TD > 10:1 = \pm 0.005$  % · TD
- Platinum:  $TD \ge 1:1 = \pm 0.025\%$

10 bar (150 psi) and 40 bar (600 psi) sensor

- Standard: TD  $\leq$  10:1 = ±0.05 %; TD > 10:1 = ±0.005 % · TD
- Platinum:  $TD \ge 1:1 = \pm 0.035 \%$

#### Measuring uncertainty for small absolute pressure measuring ranges

The smallest extended uncertainty of measurement that can delivered by our standards in the 0.001 to 35 mbar (0.0000145 to 0.5075 psi) range is 0.1 % of the reading + 0.004 mbar (0.000058 psi).

#### Temperature effect [E2]

*E2<sub>M</sub>* - *Main temperature error* 

The output changes due to the effect of the ambient temperature [IEC 62828-1/IEC 61298-3] with respect to the reference temperature [IEC 62828-1/DIN 16086]. The values specify the maximum error due to min./max. ambient or process temperature conditions.

100 mbar (1.5 psi), 250 mbar (3.75 psi) and 400 mbar (6 psi) sensor

- Standard: ± (0.07 % · TD + 0.038 %)
- Platinum: ± (0.07 % · TD + 0.038 %)
- 1 bar (15 psi), 2 bar (30 psi), 4 bar (60 psi), 10 bar (150 psi) and 40 bar (600 psi) sensor
- Standard: ± (0.065 % · TD + 0.02 %)
  Platinum: ± (0.065 % · TD + 0.02 %)
- *E2<sub>E</sub> Electronics error*
- Analog output (4 to 20 mA): 0.05 %
- Digital output (HART/PA/FF): 0 %

Resolution

Current output:  $1\,\mu A$ 

**Total error** 

The total error of the device comprises the total performance and the long-term stability effect and is calculated using the following formula:

Total error = total performance + long-term stability

#### Calculation of the total error with the Endress+Hauser Applicator

Detailed inaccuracies, e.g. for other temperature ranges or the high-temperature version of the device can be calculated with the Applicator "Sizing Pressure Performance".



#### Calculation of the diaphragm seal error with the Endress+Hauser Applicator

Diaphragm seal errors are not taken into consideration. They are calculated separately in the Applicator "Sizing Diaphragm Seal".



Long-term stability

The specifications refer to the upper range limit (URL).

#### Gauge pressure sensors

- 1 year: ± 0.05 %
- 5 years: ± 0.08 %
- I0 years: ± 0.10 %


Absolute pressure sensors

- 1 year: ± 0.05 %
- 5 years: ± 0.15 %
- 10 years: ± 0.20 %

#### Response time T63 and T90 D

#### Dead time, time constant

Representation of dead time and time constant as per IEC62828-1:



#### Dynamic behavior, current output

	Dead time (t <sub>1</sub> )	Time constant T63 $(t_2)$	Time constant T90 (t <sub>3</sub> )
Max.	90 ms	120 ms	276 ms

#### Dynamic behavior, digital output (HART electronics)

A typical burst rate of 300 ms results in the following behavior:

	Dead time (t <sub>1</sub> )		Dead time (t <sub>1</sub> ) + Time constant T90 (t <sub>3</sub> )
Min.	250 ms	370 ms	436 ms
Max.	1050 ms	1170 ms	1236 ms

#### Reading cycle

• Acyclic: max. 3/s, typically 1/s (depending on command # and number of preambles)

• Cyclic (burst): max. 3/s, typically 2/s

The device offers the BURST MODE function for cyclic value transmission via the HART communication protocol.

Cycle time (update time)

Cyclic (burst): min. 300 ms

#### Dynamic behavior PROFIBUS PA

A typical PLC cycle time of 1 s results in the following behavior:

	Dead time (t <sub>1</sub> )		Dead time $(t_1)$ + Time constant T90 $(t_3)$
Min.	125 ms	245 ms	311 ms
Max.	1325 ms	1445 ms	1511 ms

#### Read cycle (PLC)

- Acyclic: typically 25/s
- Cyclic: typically 30/s (dependent on the number and type of function blocks used in a closedcontrol loop)

#### Cycle time (update time)

Min. 200 ms

The cycle time in a bus segment in cyclic data communication depends on the number of devices, on the segment coupler used and on the internal PLC cycle time. A new measured value can be determined up to five times a second.

#### **Dynamic behavior FOUNDATION Fieldbus**

A typical configuration for the macro cycle time (host system) of 1 s results in the following behavior:

			Dead time $(t_1)$ + Time constant T90 $(t_3)$
Min.	135 ms	255 ms	321 ms
Max.	1135 ms	1255 ms	1321 ms

Reading cycle

- Acyclic: typically 10/s
- Cyclic: max. 10/s (dependent on the number and type of function blocks used in a closed-control loop)

Cycle time (update time)

Cyclic: min. 100 ms

#### Installation factors

#### Influence of installation position

 $\leq$  0.18 mbar (0.003 psi). Device rotated 180°, process connection pointing upwards.

A position-dependent zero point shift can be corrected. Please refer to the "Commissioning  $\rightarrow$  Position adjustment" section of the Operating Instructions.

Different tightening torques (e.g. for Clamp or Varivent connections) can merely cause a shift in the zero point. This effect is corrected by position adjustment during commissioning.

#### Warm-up period

- 4 to 20 mA HART: < 10 s
- PROFIBUS PA: 6 s
- FOUNDATION Fieldbus: 50 s

Response time	HART		
	<ul> <li>Acyclic: min. 330 ms, typically 590 ms (depending on command # and number of preambles)</li> <li>Cyclic (burst): min. 160 ms, typically 350 ms (depending on command # and number of preambles)</li> </ul>		
	PROFIBUS PA		
	<ul> <li>Acyclic: approx. 60 ms to 70 ms (depending on Min. Slave Interval)</li> <li>Cyclic: approx. 10 ms to 13 ms (depending on Min. Slave Interval)</li> </ul>		
	FOUNDATION Fieldbus		
	<ul> <li>Acyclic: typically 100 ms (for standard bus parameter settings)</li> <li>Cyclic: max. 20 ms (for standard bus parameter settings)</li> </ul>		
Reference operating conditions	<ul> <li>As per IEC 62828-2 / IEC 60770</li> <li>Ambient temperature T<sub>A</sub> = constant, in the range +22 to +28 °C (+72 to +82 °F)</li> <li>Humidity φ = constant, in the range: 5 to 80 % RH ± 5 %</li> <li>Ambient pressure p<sub>U</sub> = constant, in the range:860 to 1060 mbar (12.47 to 15.37 psi)</li> <li>Position of the measuring cell: horizontal ±1°</li> <li>Input of LOW SENSOR TRIM and HIGH SENSOR TRIM for lower range value and upper range value</li> <li>Span based on zero point</li> </ul>		
	<ul> <li>Span based on Zero point</li> <li>Membrane material PMP71/PMP75: AISI 316L (1.4435) or Alloy C</li> <li>Filling oil PMP71/PMP75: silicone oil</li> <li>Supply voltage: 24 V DC ±3 V DC</li> <li>Load with HART: 250 Ω</li> <li>Turn down (TD) = URL/ URV - LRV </li> </ul>		
Total performance	The performance characteristics refer to the accuracy of the device. The factors that influence the accuracy can be divided into two groups <ul> <li>Total performance of device</li> <li>Installation factors</li> </ul>		
	All of the performance characteristics meet the requirement of $\geq \pm 3$ sigma.		
	The total performance of the device comprises the reference accuracy and the ambient temperature effect and is calculated using the following formula:		
	Total performance = $\pm \sqrt{((E1)^2 + (E2)^2)}$		
	E1 = Reference accuracy		
	E2 = Ambient temperature effect		
	Calculation of E2:		
	Ambient temperature effect per ±28 °C (50 °F)		
	(Corresponds to a range of $-3$ to $+53$ °C (+27 to $+127$ °F))		
	$E2 = E2_M + E2_E$		
	E2 <sub>M</sub> = Main temperature error		
	$E2_E = Electronics error$		

# Performance characteristics for measuring devices with metal process membrane

#### Calculation of the total performance with the Endress+Hauser Applicator

Detailed inaccuracies, e.g. for other temperature ranges, can be calculated with the Applicator "Sizing Pressure Performance".



#### Calculation of the diaphragm seal error with the Endress+Hauser Applicator

Diaphragm seal errors are not taken into consideration. They are calculated separately in the Applicator "Sizing Diaphragm Seal".



#### Reference accuracy [E1]

Reference accuracy comprises the non-linearity [IEC 62828-1/DIN EN 61298-2] including the hysteresis [IEC 62828-1/DIN EN 61298-2] and the non-repeatability [IEC 62828-1/DIN EN 61298-2] in accordance with the limit point method as per [IEC 62828-1/DIN EN 60770-2]. Reference accuracy for standard up to TD 100:1, for platinum up to TD 5:1.

#### PMP71

400 mbar (6 psi) sensor

- Standard:  $\overline{\text{TD}}$  1:1 = ±0.05 %; TD > 1:1 = ±0.05 % · TD
- Platinum: TD 1:1 =  $\pm 0.025$  %; TD > 1:1 =  $\pm 0.04$  %

1 bar (15 psi) sensor

- Standard: TD  $\leq 2.5:1 = \pm 0.05$  %; TD > 2.5:1 =  $\pm 0.02$  % · TD
- Platinum: TD 1:1 = ±0.025 %; TD > 1:1 = ±0.03 %

2 bar (30 psi) sensor

- Standard:  $TD \le 5:1 = \pm 0.05$  %;  $TD > 5:1 = \pm 0.01$  % · TD
- Platinum: TD 1:1 = ±0.025 %; TD > 1:1 = ±0.03 %
- 4 bar (60 psi), 10 bar (150 psi) and 40 bar (600 psi) sensor
- Standard: TD  $\leq$  10:1 = ±0.05 %; TD > 10:1 = ±0.005 % · TD
- Platinum: TD 1:1 = ±0.025 %; TD > 1:1 = ±0.03 %

100 bar (1500 psi) sensor

- Standard:  $TD \le 10.1 = \pm 0.05$  %;  $TD > 10.1 = \pm 0.005$  % · TD
- Platinum: TD 1:1 = ±0.035 %; TD > 1:1 = ±0.04 %

400 bar (6000 psi) and 700 bar (10500 psi) sensor

- Standard:  $TD \le 5:1 = \pm 0.1$  %;  $TD > 5:1 = \pm 0.02$  % · TD
- Platinum: TD 1:1 = ±0.065 %; TD > 1:1 = ±0.09 %

PMP71 with 1-5V DC:

- 400 mbar (6 psi) to 100 bar (1500 psi) sensor, multiply values by a factor of 2
- 400 bar (6000 psi) and 700 bar (10500 psi) sensor, multiply values by a factor of 1.5

Platinum not for flush-mounted process connections G  $\frac{1}{2}$  and M20.

#### PMP75

400 mbar (6 psi) sensor Standard: TD 1:1 =  $\pm 0.15$  %; TD > 1:1 =  $\pm 0.15$  % · TD 1 bar (15 psi) sensor Standard: TD  $\leq 2.5:1 = \pm 0.075$  %; TD > 2.5:1 =  $\pm 0.03$  % · TD 2 bar (30 psi) sensor Standard: TD  $\leq 5:1 = \pm 0.075$  %; TD > 5:1 =  $\pm 0.015$  % · TD 4 bar (60 psi), 10 bar (150 psi), 40 bar (600 psi) and 100 bar (1500 psi) sensor

Standard:  $TD \le 10:1 = \pm 0.075$  %;  $TD > 10:1 = \pm 0.0075$  % · TD400 bar (6000 psi) sensor Standard:  $TD \le 5:1 = \pm 0.15$  %;  $TD > 5:1 = \pm 0.03$  % · TD

#### Measuring uncertainty for small absolute pressure measuring ranges

The smallest extended uncertainty of measurement that can delivered by our standards in the 0.001 to 35 mbar (0.0000145 to 0.5075 psi) range is 0.1 % of the reading + 0.004 mbar (0.000058 psi).

#### Temperature effect [E2]

*E2<sub>M</sub>* - *Main temperature error* 

	The output changes due to the effect of the ambient temperature [IEC 62828-1/IEC 61298-3] with respect to the reference temperature [IEC 62828-1/DIN 16086]. The values specify the maximum error due to min./max. ambient or process temperature conditions.
	400 mbar (6 psi), 1 bar (15 psi), 2 bar (30 psi) and 4 bar (60 psi) sensor $\pm$ (0.04 % $\cdot$ TD + 0.08 %)
	10 bar (150 psi) and 40 bar (600 psi) sensor ± (0.03 % · TD + 0.03 %)
	100 bar (1500 psi), 400 bar (6000 psi) and 700 bar (10500 psi) sensor $\pm$ (0.015 % $\cdot$ TD + 0.06 %)
	$E2_E$ - Electronics error
	<ul> <li>Analog output (4 to 20 mA): 0.05 %</li> <li>Digital output (HART/PA/FF): 0 %</li> <li>PMP71 with 1-5V DC: 0.18 %</li> </ul>
	The additional electronics error that occurs in the temperature range –50 to –41 °C (–58 to –42 °F) is covered by $E2_{LT}$ .
	<i>E2<sub>LT</sub> - Low temperature error</i>
	The specifications refer to the calibrated span.
	<ul> <li>-40 to +85 °C (-40 to +185 °F): 0 %</li> <li>-50 to -41 °C (-58 to -42 °F): 1.5 %</li> </ul>
Resolution	Current output: 1 μA
	Voltage output: 1 mW
Total error	The total error of the device comprises the total performance and the long-term stability effect and is calculated using the following formula:
	Total error = total performance + long-term stability
	Calculation of the total error with the Endress+Hauser Applicator
	Detailed inaccuracies, e.g. for other temperature ranges, can be calculated with the Applicator "Sizing Pressure Performance".



A0038927

# Calculation of the diaphragm seal error with the Endress+Hauser Applicator

Diaphragm seal errors are not taken into consideration. They are calculated separately in the Applicator "Sizing Diaphragm Seal".

► t

Long-term stability	The specifications refer to the upper range limit (URL).
	2 bar (30 psi) sensor • 1 year: ± 0.07 % • 5 years: ± 0.12 % • 10 years: ± 0.15 %
	All other sensors • 1 year: ± 0.05 % • 5 years: ± 0.07 % • 10 years: ± 0.10 %
Response time T63 and T90	Dead time, time constant
	Representation of dead time and time constant as per IEC62828-1:
	I A 100 % 90 % 63 %

# Dynamic behavior, current output

Туре		Sensor	Dead time $(t_1)$	Time constant T63 $(t_2)$	Time constant T90 (t <sub>3</sub> )
PMP71	Max.	<ul> <li>400 mbar (6 psi)</li> <li>≥ 1 bar (15 psi)</li> </ul>	45 ms	<ul><li>70 ms</li><li>35 ms</li></ul>	<ul><li>161 ms</li><li>81 ms</li></ul>
PMP75	Max.	PMP71 + influence of the diaphragm seal			

t<sub>1</sub> t<sub>2</sub>

t<sub>3</sub>

# Dynamic behavior, digital output (HART electronics)

A typical burst rate of 300 ms results in the following behavior:

Туре		Sensor	Dead time (t <sub>1</sub> )	Dead time (t <sub>1</sub> ) + Time constant T63 (t <sub>2</sub> )	Dead time (t <sub>1</sub> ) + Time constant T90 (t <sub>3</sub> )
PMP71	Min.	<ul> <li>400 mbar (6 psi)</li> <li>≥ 1 bar (15 psi)</li> </ul>	205 ms	<ul><li> 275 ms</li><li> 240 ms</li></ul>	<ul><li> 321 ms</li><li> 241 ms</li></ul>
	Max.	<ul> <li>400 mbar (6 psi)</li> <li>≥ 1 bar (15 psi)</li> </ul>	1005 ms	<ul><li>1075 ms</li><li>1040 ms</li></ul>	<ul><li>1121 ms</li><li>1041 ms</li></ul>
PMP75	Max.	PMP71 + influence of the diaphragm seal			

A0019786

#### Reading cycle

Acyclic: max. 3/s, typically 1/s (depending on command # and number of preambles)
Cyclic (burst): max. 3/s, typically 2/s

The device offers the BURST MODE function for cyclic value transmission via the HART communication protocol.

#### Cycle time (update time)

Cyclic (burst): min. 300 ms

#### Dynamic behavior 1-5V DC

Туре		Sensor	Dead time (t <sub>1</sub> )	Time constant T63 (t <sub>2</sub> )	Time constant T90 (t <sub>3</sub> )
PMP71	Max.	All	40 ms	70 ms	180 ms

#### Dynamic behavior PROFIBUS PA

A typical PLC cycle time of 1 s results in the following behavior:

Туре		Sensor	Dead time (t <sub>1</sub> )	Dead time $(t_1)$ + Time constant T63 $(t_2)$	Dead time $(t_1) +$ Time constant T90 $(t_3)$
PMP71	Min.	<ul> <li>400 mbar (6 psi)</li> <li>≥ 1 bar (15 psi)</li> </ul>	80 ms	<ul><li>150 ms</li><li>115 ms</li></ul>	<ul><li>196 ms</li><li>116 ms</li></ul>
	Max.	<ul> <li>400 mbar (6 psi)</li> <li>≥ 1 bar (15 psi)</li> </ul>	1280 ms	<ul><li>1350 ms</li><li>1315 ms</li></ul>	<ul><li>1396 ms</li><li>1316 ms</li></ul>
PMP75	Max.	PMP71 + influence of the diaphragm seal			

#### Read cycle (PLC)

- Acyclic: typically 25/s
- Cyclic: typically 30/s (dependent on the number and type of function blocks used in a closedcontrol loop)

#### Cycle time (update time)

Min. 200 ms

The cycle time in a bus segment in cyclic data communication depends on the number of devices, on the segment coupler used and on the internal PLC cycle time. A new measured value can be determined up to five times a second.

#### Dynamic behavior FOUNDATION Fieldbus

A typical configuration for the macro cycle time (host system) of 1 s results in the following behavior:

Туре		Sensor	Dead time (t <sub>1</sub> )	Dead time (t <sub>1</sub> ) + Time constant T63 (t <sub>2</sub> )	Dead time (t <sub>1</sub> ) + Time constant T90 (t <sub>3</sub> )
PMP71	Min.	<ul> <li>400 mbar (6 psi)</li> <li>≥ 1 bar (15 psi)</li> </ul>	90	<ul><li>160</li><li>125</li></ul>	■ 206 ■ 126
	Max.	<ul> <li>400 mbar (6 psi)</li> <li>≥ 1 bar (15 psi)</li> </ul>	1090	<ul><li>1160</li><li>1125</li></ul>	<ul><li>1206</li><li>1126</li></ul>
PMP75	Max.	PMP71 + influence of the diaphragm seal			

Reading cycle

- Acyclic: typically 10/s
- Cyclic: max. 10/s (dependent on the number and type of function blocks used in a closed-control loop)

*Cycle time (update time)* Cyclic: min. 100 ms

Installation factors

#### Influence of installation position

PMP71: Device rotated 180°, process connection pointing upwards. The value is doubled for devices with inert oil.

- Process connection thread G 1 A, G 1 ½, G 2, 1 ½ MNPT, 2 MNPT, M 44x1.25, EN/DIN, ASME and JIS flanges: ≤ 10 mbar (0.15 psi).
- Process connection thread: G  $\frac{1}{2}$ ,  $\frac{1}{2}$  MNPT, JIS G  $\frac{1}{2}$ , JIS R  $\frac{1}{2}$ , M20x1.5:  $\leq$  4 mbar (0.06 psi).

A position-dependent zero point shift can be corrected. Please refer to the "Commissioning  $\rightarrow$  Position adjustment" section of the Operating Instructions.

Different tightening torques (e.g. for Clamp or Varivent connections) can merely cause a shift in the zero point. This effect is corrected by position adjustment during commissioning.

#### Warm-up period


- 4 to 20 mA HART: < 10 s
- PROFIBUS PA: 6 s
- FOUNDATION Fieldbus: 50 s

	IIIStallation		
General installation instructions	<ul> <li>For PMP75: →  120 "Installation instructions" section.</li> <li>A position-dependent zero point shift can be corrected directly at the device via operating keys, and also in hazardous areas in the case of devices with external operation. Diaphragm seals also shift the zero point, depending on the installation position →  120.</li> <li>The device housing can be rotated up to 380°.</li> <li>Endress+Hauser offers a mounting bracket for installing the device on pipes or walls →  120.</li> <li>Use flushing rings for flange and cell diaphragm seals if buildup or clogging can be expected at the diaphragm seal connection. The flushing ring can be fitted between the process connection and diaphragm seal. Material buildup in front of the process isolating diaphragm can be flushed away, and the pressure chamber vented, via the two lateral flushing holes.</li> <li>When measuring in media containing solids, such as dirty liquids, installing separators and drain valves is useful for capturing and removing sediment.</li> <li>Point the cable and connector downwards where possible to prevent moisture from entering (e.g. rain or condensation water).</li> </ul>		
Measuring arrangement for devices without diaphragm seals – PMC71, PMP71	Cerabar S devices without diaphragm seals are mounted in accordance with the same guidelines as a manometer (DIN EN 837-2). We recommend the use of shutoff devices and siphons. The orientatio depends on the measuring application.		
	Pressure measurement in gases		
	Mount the Cerabar S with shutoff device above the tapping point so that any condensate can flow into the process.		
	Pressure measurement in vapors		
	Use siphons for pressure measurement in steam. The siphon reduces the temperature to almost ambient temperature. Fill the siphon with liquid before commissioning. Preferably mount the Cerabar S with the siphon below the tapping point.		
	Advantages: • defined water column only causes minimal/negligible measured errors • only minimal/negligible thermal effects on the device		
	Mounting above the tapping point is also possible. Observe the max. permitted ambient temperatur of the transmitter!		
	Pressure measurement in liquids		
	Mount the Cerabar S with shutoff device below or at the same level as the tapping point.		
	Level measurement		
	<ul> <li>Mount the Cerabar S below the lowest measuring point.</li> <li>Do not install the device in the following positions: In the filling curtain, in the tank outlet or at a point in the vessel which could be affected by pressure pulses from an agitator or a pump.</li> <li>The calibration and functional test can be carried out more easily if you mount the device downstream from a shutoff device.</li> </ul>		
Measuring arrangement for devices with diaphragm seals – PMP75	→ 🗎 120		
Orientation	The orientation may cause a zero point shift.		
	This position-dependent zero point shift can be corrected directly at the device via the operating key and also in hazardous areas in the case of devices with external operation (position adjustment).		

# Installation

#### Wall and pipe mounting, transmitter (optional)

Endress+Hauser offers the following mounting bracket for installing the device on pipes or walls:




Ordering information:

- Product Configurator, order code for "Accessories enclosed", option "PA"
  For devices with separate housing (can be ordered using the order code for "Additional options 2") included in the scope of delivery
- Can be ordered as a separate accessory (part no.: 71102216).

For further details, see  $\rightarrow \implies 103$ .

Wall and pipe mounting, valve manifold (optional)	
	For the technical data (such as the dimensions or order numbers for screws), see the document SD01553P/00/EN.
	Ordering information: Product Configurator, order code for "Accessories enclosed", option "PK"
Heat insulation – PMC71 high-temperature version	The PMC71 high-temperature version must only be insulated up to a certain height. The maximum permitted insulation height is indicated on the devices and applies to an insulation material with a heat conductivity $\leq 0.04$ W/(m x K) and to the maximum permitted ambient and process temperature (see table below). The data were determined under the most critical application "quiescent air".
	The data were determined under the most critical application "quiescent air".



- A Ambient temperature range
- B Process temperature
- 1 Insulation height
- 2 Insulation material

	Temperature
Ambient temperature range	≤ 70 °C (158 °F)
Process temperature	≤ 150 °C (302 °F)

Mounting of PVDF screw-in fittings

## **WARNING**

#### Risk of damage to process connection!

Risk of injury!

PVDF threaded process connections must be mounted with the mounting bracket supplied!

The mounting bracket can be installed on pipes with a diameter of  $1\frac{1}{4}$ " to 2" or on walls.

Dimensions  $\rightarrow \square 52$ .

## "Separate housing" version


With the "separate housing" version, you are able to mount the housing with the electronics insert at a distance from the measuring point. This version facilitates trouble-free measurement

- Under particularly difficult measuring conditions (at installation locations that are cramped or difficult to access)
- If rapid cleaning of the measuring point is required and
- If the measuring point is exposed to vibrations.
- You can choose between different cable versions:
- PE: 2 m (6.6 ft), 5 m (16 ft) and 10 m (33 ft)
- FEP: 5 m (16 ft).

Ordering information: Product Configurator, order code for "Additional options 2", version "G".

#### Dimensions $\rightarrow \square 103$

In the case of the "separate housing" version, the sensor is delivered with the process connection and cable ready mounted. The housing and a mounting bracket are enclosed as separate units. The cable is provided with a socket at both ends. These sockets are simply connected to the housing and the sensor.



Degree of protection for the process connection and sensor with the use of

- FEP cable:
  - IP 69<sup>1)</sup>
  - IP 66 NEMA 4/6P
  - IP 68 (1.83 mH<sub>2</sub>O for 24 h) NEMA 4/6P
- PE cable:
  - IP 66 NEMA 4/6P
  - IP 68 (1.83 mH<sub>2</sub>O for 24 h) NEMA 4/6P

Technical data of the PE and FEP cable:

- Minimum bending radius: 120 mm (4.72 in)
- Cable extraction force: max. 450 N (101.16 lbf)
- Resistance to UV light


Use in hazardous area:

- Intrinsically safe installations (Ex ia/IS)
- FM/CSA IS: for Div. 1 installation only

<sup>1)</sup> Designation of the IP protection class according to DIN EN 60529. Previous designation "IP69K" according to DIN 40050 Part 9 is no longer valid (standard withdrawn on November 1, 2012). The tests required by both standards are identical.

#### Reduction of the installation height

If the separate housing is used, the installation height of the process connection is reduced compared to the dimensions of the standard version.




#### Turning the housing

The housing can be rotated up to 380° by loosening the Allen screw.

#### Your benefits

- Easy mounting due to optimum alignment of housing
- Good, accessible device operation
- Optimum readability of the onsite display (optional).



Version	PMC71 High-temperature version	PMC71	PMP71	PMP75
Without LCD display	-20 to +70 °C	−40 to +85 ℃ (− 40 to +185 ℉)	-50 to +85 °C (-58 to +185 °F) <sup>1)</sup> -60 to +85 °C (-76 to +185 °F) <sup>2)</sup>	
With LCD display <sup>3)</sup>	(−4 to +158 °F)	-20 to +70 °C (-4 to +158 °F)		
With M12 plug , elbowed		-25 to +85 °C (-13 to +185 °F)		
With separate housing	_	−20 to +60 °C (−4	to +140 °F)	-
Diaphragm seal systems <sup>4)</sup>	_	_	_	→ 🗎 121
MID parts certificate	_	_	−25 to +55 ℃ (−13 to +131 ℉)	_

# Environment

#### Ambient temperature range

1) If the temperature is below -40 °C (-40 °F), the chance of failure increases. Product Configurator, order code for "Test, Certificate" option "JN".


2) If the temperature is below -40 °C (-40 °F), the chance of failure increases. Product Configurator, order code for "Test, Certificate" option "JT".

- 3) Extended temperature application range (-50 to +85 °C (-58 to +185 °F)) with restrictions in optical properties, such as display speed and contrast
- 4) Ambient temperature range and process temperature range are mutually dependent see "Heat insulation" section → 
  □ 121

For high-temperature applications, either a PMP75 with a temperature isolator or with a capillary can be used. If vibrations also occur in the application, Endress+Hauser recommends using a PMP75 with a capillary. If a PMP75 with a temperature isolator or capillary is used, we recommend a suitable bracket for mounting (see "Wall and pipe mounting" section  $\rightarrow \cong 42$ ).

#### PMP71: Ambient temperature T<sub>a</sub> depending on the process temperature T<sub>p</sub>

The process connection must be fully insulated for ambient temperatures below -40 °C (-40 °F).



1 Insulation material

	Hazardous area
	<ul> <li>For devices for use in hazardous areas, see Safety Instructions, Installation or Control Drawing →  □ 135.</li> <li>Pressure measuring devices that have the usual explosion protection certificates (e.g. ATEX-/ CSA-/FM-/IEC Ex,) can be used in hazardous areas at ambient temperatures down to -50 °C (-58 °F) (order code for "Test, Certificate" option "JN"). The functionality of the explosion protection is also guaranteed for ambient temperatures down to -50 °C (-58 °F).</li> <li>Pressure measuring devices that have the usual explosion protection certificates (e.g. ATEX-/ IEC Ex, etc.) can be used in hazardous areas at ambient temperatures down to -60 to +85 °C (-76 to +185 °F) (order code for "Test, Certificate" option "JT"). The functionality of the explosion protection is also guaranteed for ambient temperatures down to -60 to +85 °C (-76 to +185 °F) (order code for "Test, Certificate" option "JT"). The functionality of the explosion protection is also guaranteed for ambient temperatures down to -60 to +85 °C (-76 to +185 °F), explosion protection is guaranteed by the housing in the case of flameproof enclosure (Ex d) type of protection. The functionality of the transmitter cannot be fully guaranteed.</li> </ul>
Storage temperature range	<ul> <li>-40 to +90 °C (-40 to +194 °F)</li> <li>Option -50 to +90 °C (-58 to +194 °F) order code 580 "Test, Certificate" option "JN". If the temperature is below -40 °C (-40 °F), the probability of a failure increases.</li> <li>Option -60 to +90 °C (-76 to +194 °F) order code 580 "Test, Certificate" option "JT". If the temperature is below -40 °C (-40 °F), the probability of a failure increases.</li> <li>Local display: -40 to +85 °C (-40 to +185 °F)</li> <li>Separate housing: -40 to +60 °C (-40 to +140 °F)</li> <li>Devices with PVC-armored capillary: -25 to +80 °C (-13 to +176 °F)</li> </ul>
Degree of protection	Depends on the deployed ■ housing: →  □ 53 ■ separate housing: → □ 103
Climate class	Class 4K4H (air temperature: -20 to +55 °C (-4 to +131 °F), relative humidity: 4 to 100 %) fulfilled as per DIN EN 60721-3-4 (condensation possible. With PMC71, avoid condensate in the device.)
Electromagnetic compatibility	<ul> <li>Electromagnetic compatibility as per EN 61326 and NAMUR recommendation EMC (NE21).</li> <li>With enhanced immunity against electromagnetic fields as per EN 61000-4-3: 30 V/m with closed cover (for devices with T14 housing) Increased interference immunity with 30 V/m not available for 1-5V DC. EMC interference immunity for 1-5V DC: 10 V/m</li> <li>Maximum deviation: &lt; 0.5 % of span</li> <li>All EMC measurements were performed with a turn down (TD) = 2:1.</li> <li>Class E3 as per OIML R75-2</li> <li>For further details refer to the Declaration of Conformity.</li> </ul>

Vibration resistance	Device/accessory	Test standard	Vibration resistance
	PMC71 <sup>1)</sup>	GL	Guaranteed for
	PMP71	-	3 to 25 Hz: ±1.6 mm (0.063 in); 25 to 100 Hz: 4 g
	PMP75 <sup>2)3)</sup>		in all 3 axes
	With mounting bracket	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 60 Hz: ±0.15 mm (0.0059 in); 60 to 500 Hz: 2 g in all 3 axes
	PMP71 with MID parts certificate	OIML R117-1	Class M3

Not for high-temperature version with Ex d[ia], CSA XP or FM XP With a luminum T14 housing only 1)

2)

For applications with very high temperatures, a PMP75 with either a temperature isolator or a capillary can be used. If vibrations also occur in the application, Endress+Hauser recommends using a PMP75 with a 3) capillary. If a PMP75 with a temperature isolator or capillary is used, it must be mounted with a mounting bracket

# Oxygen applications

Oxygen and other gases can react explosively to oils, grease and plastics, such that, among other things, the following precautions must be taken:

- All components of the system, such as measuring devices, must be cleaned in accordance with the BAM requirements.
- Depending on the materials used, a certain maximum temperature and a maximum pressure must not be exceeded for oxygen applications.

The devices that are suitable for gaseous oxygen applications are indicated by  $p_{\text{max}}$  in the following table.

HB = Cleaned for oxygen service

Order code for devices <sup>1)</sup> , cleaned for oxygen applications	p <sub>max</sub> for oxygen applications	T <sub>max</sub> for oxygen applications
PMC71 - * * * * * * 2 * * or PMC71 - * * * * * * A * * HB, Devices with sensors, nominal value < 10 bar (150 psi)	Overpressure limit (OPL) <sup>2)3)</sup> of the sensor	60 °C (140 °F)
PMC71 - * * * * * * 2 * *, PMC71 - * * * * * * A * * HB, Devices with sensors, nominal value ≥ 10 bar (150 psi)	40 bar (600 psi)	60 ℃ (140 ℉)
PMP71 - * * * * * * * * N * * or PMP71 - * * * * * * * F * * HB	Depends on the lowest-rated element, with regard to pressure, of the selected components: overpressure limit (OPL) of the sensor, process connection (1.5 x PN) or fill fluid (80 bar (1 200 psi))	60 ℃ (140 ℉)
PMP75 - * * * * * * * * * N * * or PMP75 - * * * * * * * * * F * * HB	Depends on the lowest-rated element, with regard to pressure, of the selected components: overpressure limit (OPL) of the sensor, process connection $(1.5 \text{ x PN})$ or fill fluid (80 bar $(1200 \text{ psi}))$	60 ℃ (140 ℉)

1) Devices only, not accessories or enclosed accessories.

3) PMC71 with PVDF thread or PVDF flange: only mount with the enclosed mounting bracket. MWP 10 bar (150 psi), OPL max. 15 bar (225 psi). Process temperature range –10 to +60 °C (+14 to +140 °F)

PWIS-free applications	Special cleaning of the transmitter to remove paint-wetting substances, for use in paint shops, for instance. Ordering information:		
	Product Configurator, order code for "Seal", option "L" or "M".		
Ultrapure gas applications	Endress+Hauser also offers device for special applications, such as for ultrapure gas, which have been cleaned of oil and grease. No special restrictions regarding the process conditions apply to these devices.		
	Ordering information: • Product Configurator, order code for "Seal" or • Product Configurator, order code for "Fill fluid".		
Hydrogen applications	A <b>ceramic</b> process isolating diaphragm or a <b>gold-coated</b> metal process isolating diaphragm offers universal protection against hydrogen diffusion, both in gas applications and in applications with aqueous solutions.		
	Applications with hydrogen in aqueous solutions		
	A <b>gold/rhodium-coated</b> metal process isolating diaphragm (AU/Rh) offers effective protection against hydrogen diffusion.		
Operation in very corrosive	PMP75:		
environment	For corrosive environments (e.g. maritime environment / coastal areas), Endress+Hauser recommends the use of a PVC or PTFE armor for the capillaries ( $\rightarrow \square$ 108).		

<sup>2)</sup> Product Configurator, order code for "Sensor range; sensor overpressure limit (= OPL)"

	Process
Process temperature limits	For oxygen applications $\rightarrow \square 48$
	PMC71 (with ceramic process membrane)
	<ul> <li>-25 to +125 °C (-13 to +257 °F)</li> <li>High-temperature version: -25 to +150 °C (-13 to +302 °F); Product Configurator, order code for "Additional options 1", option "T".</li> <li>For saturated steam applications, use a device with a metal process membrane, or provide a sinhon.</li> </ul>

- For saturated steam applications, use a device with a metal process membrane, or provide a siphon for temperature isolation when installing.
- Observe the process temperature range of the seal in the following table.

Seal	Notes	Process temperature range	Option <sup>1)</sup>
FKM Viton	-	-25 to +125 °C (-13 to +257 °F)/ 150 °C (302 °F) <sup>2)</sup>	A, L
EPDM 70	FDA 21CFR177.2600	-40 to +125 °C (-40 to +257 °F)/ 150 °C (302 °F) <sup>2)</sup>	В
EPDM 331	FDA 21CFR177.2600; 3A Class II; USP Class VI DVGW (UBA "KTW", W270), NSF61	-20 to +125 °C (-4 to +257 °F)/ 150 °C (302 °F) <sup>2)</sup>	B <sup>3)</sup>
FFKM Perlast G75LT	-	-20 to +125 °C (-4 to +257 °F)/ 150 °C (302 °F) <sup>2)</sup>	С
Kalrez, Compound 4079	-	+5 to +125 °C (+41 to +257 °F)/ 150 °C (302 °F) <sup>2)</sup>	D, M
Chemraz, Compound 505	-	-10 to +125 °C (+14 to +257 °F)/ 150 °C (302 °F) <sup>2)</sup>	
HNBR	FDA 21CFR177.2600; 3A Class II; KTW; AFNOR; BAM	−25 to +125 °C (−13 to +257 °F)	F <sup>4)</sup>
NBR	_	-10 to +100 °C (+14 to +212 °F)	F
FKM Viton	FDA 21CFR177.2600	-5 to +125 °C (+23 to +257 °F)	G
FKM Viton	cleaned of oil and grease	-10 to +125 °C (+14 to +257 °F)/ 150 °C (302 °F) <sup>2)</sup>	
FKM Viton	cleaned for oxygen service	-10 to +60 °C (+14 to +140 °F)	2 or A <sup>5)</sup>

They may be exceeded for a short time (e.g. for cleaning).

1) Product Configurator, order code for "Seal"

2) 150 °C (302 °F) for high-temperature version

3) In combination with order code for "Additional options 1" option "F" or with order code for "Process connection" option "MP", "MR", "TD", "TF", "TK" or "TR"

4) These seals are used for devices with 3A-approved process connections.

5) with option "HB", see Product Configurator, order code for "Service"

Applications with changes in temperature

Extreme changes in temperature can result in temporary measuring errors. Temperature compensation takes place after a few minutes. Internal temperature compensation is faster the smaller the change in temperature and the longer the time interval.



For further information please contact your local Endress+Hauser Sales Center.

#### PMP71 (with metal process membrane)

Designation	Limits
Process connections with internal process membrane	-40 to +125 °C (-40 to +257 °F) (150 °C (302 °F) for max. one hour)
Process connections with flush membrane <sup>1)</sup>	-40 to +100 °C (-40 to +212 °F)
Process connections with flush membrane, G ½ A, M20x1.5	-20 to +85 °C (-4 to +185 °F)

1) Process connection 1A, 1B, 1N, 1P: seal supplied up to -20 °C (-4 °F) process temperature

#### PMP71 (with metal process membrane) with MID parts certificate

-25 to +55 °C (-13 to +131 °F)

#### PMP75 (with diaphragm seal)

- Please observe the maximum gauge pressure and maximum temperature.

*Devices with PTFE-coated process membrane* 


The non-stick coating has excellent gliding properties and is used to protect the process membrane against abrasive media.

#### NOTICE

The device can be damaged if the PTFE foil is used for anything other than the designated purpose!

The PTFE foil used is designed to protect the unit against abrasion. It does not provide protection
against corrosive media.


Application of 0.25 mm (0.01 in) PTFE foil on AISI 316L (1.4404/1.4435) process membrane - see the following graphic:



For vacuum applications:  $p_{abs} \le 1$  bar (14.5 psi) to 0.05 bar (0.725 psi) up to max. +150 °C (302 °F).

Process temperature limits of capillary armoring: PMP75

- 316L: No restrictions
- PTFE: No restrictions
- PVC: See the following diagram



#### **Pressure specifications**

#### **WARNING**

The maximum pressure for the measuring device depends on the lowest-rated element with regard to pressure.

- For pressure specifications, see the "Measuring range" section and the "Mechanical construction" section.
- ► The measuring device must be operated only within the specified limits!
- MWP (maximum working pressure): The MWP (maximum working pressure) is specified on the nameplate. This value refers to a reference temperature of +20 °C (+68 °F) and may be applied to the device for an unlimited time. Observe the temperature dependency of the MWP. For the pressure values permitted at higher temperatures for flanges, please refer to standards EN 1092-1 (with regard to their stability-temperature property, the materials 1.4435 and 1.4404 are grouped together under EN 1092-1; the chemical composition of the two materials can be identical.), ASME B 16.5a, JIS B 2220 (the latest version of the standard applies in each case).
- ➤ The test pressure corresponds to the over pressure limit of the individual sensors (OPL = 1.5 x MWP (formula does not apply to the PMP71 or PMP75 with a 40 bar (600 psi) or 100 bar (1500 psi) measuring cell)) and may be applied only for a limited period of time to prevent any lasting damage.
- The Pressure Equipment Directive (2014/68/EU) uses the abbreviation "PS". The abbreviation "PS" corresponds to the MWP (maximum working pressure) of the measuring device.
- In the case of sensor range and process connections where the over pressure limit (OPL) of the process connection is smaller than the nominal value of the sensor, the device is set at the factory, at the very maximum, to the OPL value of the process connection. If you want to use the entire sensor range, select a process connection with a higher OPL value (1.5 x PN; MWP = PN)
  - In oxygen applications, the values for " $p_{max}$  and  $T_{max}$  for oxygen applications must not be exceeded  $\rightarrow \cong 48$ .
- Devices with ceramic process isolating diaphragm: Avoid steam hammering! Steam hammering can cause zero point drifts. Recommendation: Residue (water droplets or condensation) may remain on the process isolating diaphragm following SIP cleaning and can result in local steam hammering the next time steam cleaning takes place. In practice, drying the process isolating diaphragm (e.g. by blowing off excess moisture) has proven to be a successful way of avoiding steam hammering.

#### **Burst pressure**

Device	Measuring range	Burst pressure
PMP71 <sup>1)</sup>	400 mbar (6 psi)10 bar (150 psi)	100 bar (1450 psi)
	40 bar (600 psi)	250 bar (3625 psi)
	100 bar (1 500 psi)	1000 bar (14500 psi)
	400 bar (6 000 psi)	2000 bar (29000 psi)
	700 bar (10 500 psi)	2 800 bar (40 600 psi)

1) Excluding PMP75 with mounted diaphragm seal system, PMC71 with ceramic membrane, and the universal adapter process connection.

# Mechanical construction

For the dimensions, see the Product Configurator: www.endress.com

Search for product  $\rightarrow$  click "Configuration" to the right of the product image  $\rightarrow$  after configuration click "CAD"

The following dimensions are rounded values. For this reason, the dimensions may deviate from the values on www.endress.com.

#### Device height

#### The device height is calculated from

- the height of the housing
- the height of optional mounted parts such as temperature isolators or capillaries
- the height of the relevant process connection.

The individual heights of the components can be found in the following sections. To calculate the device height, simply add up the individual heights of the components. If necessary, the installation space (the space used to install the device) must also be taken into account. You can use the following table for this:

Section	Page	Elevation	Example
Height of housing	→ 🖺 53 ff.	(A)	I I
Optional mounted parts	→ 🖺 77	(B)	
Process connections	→ 🗎 56	(H)	
Installation space	-	(I)	
Device height			

#### 

Material		Degree of protection	Cable entry	Weight in kg (l	Weight in kg (lb)	
Housing	Cover seal			with display	with display without display	
		IP66/67 NEMA 6P	M20 gland			А
		IP66/67 NEMA 6P	G ½" thread			В
	EPDM	IP66/67 NEMA 6P	NPT ½" thread			С
Aluminum	EPDIM	IP66/67 NEMA 6P	M12 plug	1.2 (2.65)	1 1 (2 (2)	D
Aluminum		IP66/67 NEMA 6P	7/8" plug	1.2 (2.65)	1.1 (2.43)	E
		IP65 NEMA 4	HAN7D plug 90 degrees			F
	FVMQ	IP66/67 NEMA 6P	M20 gland			G
	FVMQ	IP66/67 NEMA 6P	NPT ½" thread			Н
		IP66/67 NEMA 6P	M20 gland	_	2.0 (4.41)	1
		IP66/67 NEMA 6P	G ½" thread			2
	EPDM	IP66/67 NEMA 6P	NPT ½" thread			3
2161	EPDIM	IP66/67 NEMA 6P	M12 plug	2.1.(4.62)		4
316L		IP66/67 NEMA 6P	7/8" plug	2.1 (4.63)		5
		IP65 NEMA 4	HAN7D plug 90 degrees			6
	FVMQ	IP66/67 NEMA 6P	M20 gland			7
	FVMQ	IP66/67 NEMA 6P	NPT ½" thread			8

1) Product Configurator, order code for "Housing, cover seal, cable entry, degree of protection"

Material		Degree of protection <sup>1)</sup>	Cable entry	Weight in kg (lt	Weight in kg (lb)	
Housing	Cover seal			with display	without display	
		IP66/68 NEMA 6P	M20 gland			R
		IP66/68 NEMA 6P	G ½" thread			S
316L	EPDM	IP66/68 NEMA 6P	NPT ½" thread	1.2 (2.65)	1.1 (2.43)	Т
		IP66/68 NEMA 6P	M12 plug			U
		IP66/68 NEMA 6P	7/8" plug			V


1) Degree of protection IP 68: 1.83  $mH_2O$  for 24 h

2) Product Configurator, order code for "Housing, cover seal, cable entry, degree of protection"

## PMC71: height H

Process connection	Height H		
	Standard	Ex d version	
FNPT1/2 MNPT1/2 MNPT1/2 FNPT1/4 G1/2 M20x1.5 B0202 B0203	28 mm (1.1 in)	94 mm (3.7 in)	
MNPT1-1/2 MNPT2 G1-1/2 G2 M44x1.25	59 mm (2.32 in)	125 mm (4.92 in)	
Flanges	83 mm (3.27 in)	150 mm (5.91 in)	
Hygienic process connections	90 mm (3.54 in)	156 mm (6.14 in)	

Process connection	Height H	
	High-temperature version	Ex d version including high-temperature version
FNPT1/2 MNPT1/2 MNPT1/2 FNPT1/4 G1/2 G1/2 M20x1.5 B0202 B0203	107 mm (4.21 in)	173 mm (6.81 in)
MNPT1-1/2 MNPT2 G1-1/2 G2 M44x1.25	59 mm (2.32 in)	125 mm (4.92 in)
Flanges	83 mm (3.27 in)	150 mm (5.91 in)
Hygienic process connections	90 mm (3.54 in)	156 mm (6.14 in)




Item	Designation	Material	Weight 1)	Approval <sup>2)</sup>	Option <sup>3)</sup>
			kg (lb)	-	
		AISI 316L		CRN	GA
		Alloy C276 (2.4819)		CRN	GB
A	Thread ISO 228 G ½" A EN 837	Monel (2.4360)		-	GC
	1111Eau 150 220 G 72 A EN 657	<ul> <li>PVDF</li> <li>Only mount with a mounting bracket (included)</li> <li>MWP 10 bar (150 psi), OPL max. 15 bar (225 psi)</li> <li>Process temperature range: -10 to +60 °C (+14 to +140 °F)</li> </ul>		-	GD
		AISI 316L	0.60 (1.32)	CRN	GE
В	Thread ISO 228 G ½" A, G ¼" (female)	Alloy C276 (2.4819)		CRN	GF
		Monel (2.4360)		-	GG
		AISI 316L		CRN	GH
С	Thread ISO 228 G ½" A, Bore 11.4 mm (0.45 in)	Alloy C276 (2.4819)		CRN	GJ
	Jore 11.4 mm (0.45 m)	Monel (2.4360)		-	GK

1) Total weight consisting of the sensor assembly and the process connection.

2) CSA approval: Product Configurator, order code for "Approval"

# **Thread ANSI**




Item	Designation	Material	Weight 1)	Approval <sup>2)</sup>	Option <sup>3)</sup>
			kg (lb)	_	
		AISI 316L		CRN	RA
A	ANSI ½" MNPT, ¼" FNPT	Alloy C276 (2.4819)	_	CRN	RB
		Monel (2.4360)		-	RC
		AISI 316L		CRN	RD
В	ANSI ½" MNPT, Bore 11.4 mm (0.45 in)	Alloy C276 (2.4819)		CRN	RE
в		Monel (2.4360)	0.60 (1.32)	-	RF
С	ANSI ½" MNPT, Bore 3 mm (0.12 in)	<ul> <li>PVDF</li> <li>Only mount with a mounting bracket (included)</li> <li>MWP 10 bar (150 psi), OPL max. 15 bar (225 psi)</li> <li>Process temperature range: +10 to +60 °C (+14 to +140 °F)</li> </ul>	0.00 (1.32)	-	RG
		AISI 316L	1	CRN	RH
D	ANSI ½" FNPT Bore 11.4 mm (0.45 in)	Alloy C276 (2.4819)	7	CRN	RJ
	· · ·	Monel (2.4360)		-	RK

Total weight consisting of the sensor assembly and the process connection. CSA approval: Product Configurator, order code for "Approval" 1)

2)

#### Process connections for PMC71 with internal process membrane




Item	Designation	Material	Weight <sup>1)</sup>	Option <sup>2)</sup>
			kg (lb)	
А	JIS B0202 G ½" (male)	AISI 316L	0.60 (1.32)	GL
В	JIS B0203 R ½" (male)	AISI 510L	0.00 (1.52)	RL

1) Total weight consisting of the sensor assembly and the process connection.

2) Product Configurator, order code for "Process connection"

### Thread DIN 13




Item	Designation	Material	Weight <sup>1)</sup>	Option <sup>2)</sup>
			kg (lb)	
А	DIN 13 M20 x 1.5, EN 837 3 mm (0.12 in)	AISI 316L		GP
		Alloy C276 (2.4819)	0.60 (1.32)	GQ
В	DIN 13 M20 x 1.5 11.4 mm (0.45 in)	AISI 316L		GR

1) Total weight consisting of the sensor assembly and the process connection.

#### Process connections for PMC71 with flush membrane


Thread DIN 13




Designation	Material	Weight	Option <sup>1)</sup>
		kg (lb)	
DIN 13 M44 x 1.25	AISI 316L	0.63 (1.39)	1R
CT NIA4 Y 1'72	Alloy C276 (2.4819)	(1.57)	15


1) Product Configurator, order code for "Process connection"

# Thread ISO 228 G



Item	Designation	Material	Weight	Option <sup>1)</sup>
			kg (lb)	
A 7		AISI 316L	0.8 (1.76)	1G
	Thread ISO 228 G 1 ½" A	Alloy C276 (2.4819)	0.9 (1.76)	1H
		Monel (2.4360)	0.8 (1.76)	1J
		AISI 316L	1.2 (2.65)	1K
В	Thread ISO 228 G 2" A	Alloy C276 (2.4819)	1.2 (2.65)	1L
		Monel (2.4360)	1.1 (2.43)	1M







Item	Designation	Material	Weight <sup>1)</sup>	Approval <sup>2)</sup>	Option <sup>3)</sup>
			kg (lb)		
		AISI 316L (CRN)		CRN	2D
А	ANSI 1 ½" MNPT	Alloy C276 (2.4819) (CRN)	0.80 (1.76)	CRN	2E
		Monel (2.4360)		-	2F
		AISI 316L (CRN)		CRN	2G
В	ANSI 2" MNPT	Alloy C276 (2.4819) (CRN)	1.20 (2.65)	CRN	2H
		Monel (2.4360)		-	2J

Total weight consisting of the sensor assembly and the process connection. CSA approval: Product Configurator, order code for "Approval" 1) 2) 3)

Process connections for PMC71 with flush membrane








Flange	lange									Weight <sup>1)</sup>	Option <sup>2)</sup>
Material	Nominal diameter	Nominal pressure	Form	D	b	g	Quantity	<b>g</b> <sub>2</sub>	k		
				mm	mm	mm		mm	mm	kg (lb)	
AISI 316L	DN 25	PN 10-40	B1	115	18	68	4	14	85	1.9 (4.19)	BA
AISI 316L	DN 32	PN 10-40	B1	140	18	78	4	18	100	2.5 (5.51)	СР
AISI 316L	DN 40	PN 10-40	B1	150	18	88	4	18	110	3.0 (6.62)	CQ
AISI 316L	DN 50	PN 10-40	B1	165	20	102	4	18	125	3.5 (7.72)	B3
PVDF <sup>3)</sup>	DN 50	PN 10-16	B1	165	21.4	102	4	18	125	1.4 (3.09)	BR
AISI 316L	DN 50	PN 63	B2	180	26	102	4	22	135	4.6 (10.14)	C3
PVDF <sup>3)</sup>	DN 80	PN 10-16	B1	200	21.4	138	8	18	160	1.9 (4.19)	BS
AISI 316L	DN 80	PN 10-40	B1	200	24	138	8	18	160	5.8 (12.79)	B4

1) Total weight consisting of the sensor assembly and the process connection.

2) Product Configurator, order code for "Process connection"

3) MWP 10 bar (150 psi), OPL max. 15 bar (225 psi); process temperature range: -10 to +60 °C (+14 to +140 °F)



#### ASME flanges, connection dimensions in accordance with ASME B 16.5, raised face RF

Flange						Boltholes			Weight 1)	Approval <sup>2)</sup>	Option <sup>3)</sup>
Material	Nominal diameter	Class	D	b	g	Quantity	<b>g</b> <sub>2</sub>	k			
	[in]	[lb./sq.in]	[in]	[in]	[in]		[in]	[in]	[kg (lb)]		
AISI 316/316L 4)	1	150	4.25	1.18	2	4	0.62	3.12	2.3 (5.07)	-	AA <sup>5)</sup>
AISI 316/316L 4)	1	300	4.88	1.18	2	4	0.75	3.5	8.5 (18.74)	-	AB 5)
AISI 316/316L 4)	1 1/2	150	5	0.69	2.88	4	0.62	3.88	2.1 (4.63)	CRN	AE
AISI 316/316L 4)	1 1/2	300	6.12	0.81	2.88	4	0.88	4.5	3.3 (7.28)	CRN	AQ
AISI 316/316L 4)	2	150	6	0.75	3.62	4	0.75	4.75	3.1 (6.84)	CRN	AF
ECTFE <sup>6)</sup>	2	150	6	0.75	3.62	4	0.75	4.75	3.1 (6.84)	CRN	JR
PVDF <sup>7)</sup>	2	150	6	0.75	3.62	4	0.75	4.75	0.5 (1.1)	-	A3
AISI 316/316L 4)	2	300	6.5	0.88	3.62	8	0.75	5	4.0 (8.82)	CRN	AR
AISI 316/316L 4)	3	150	7.5	0.94	5	4	0.75	6	5.7 (12.57)	CRN	AG
ECTFE <sup>6)</sup>	3	150	7.5	0.94	5	4	0.75	6	5.7 (12.57)	CRN	JS
PVDF <sup>7)</sup>	3	150	7.5	0.94	5	4	0.75	6	1.6 (3.53)	-	A4
AISI 316/316L 4)	3	300	8.25	1.12	5	8	0.88	6.62	7.5 (16.54)	CRN	AS
AISI 316/316L 4)	4	150	9	0.94	6.19	8	0.75	7.5	7.6 (16.76)	CRN	AH
ECTFE <sup>6)</sup>	4	150	9	0.94	6.19	8	0.75	7.5	7.8 (17.20)	CRN	JT
AISI 316/316L 4)	4	300	10	1.25	6.19	8	0.88	7.88	12.4 (27.34)	CRN	AT

1) Total weight consisting of the sensor assembly and the process connection.

2) CSA approval: Product Configurator, order code for "Approval"

3) Product Configurator, order code for "Process connection"


4) Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual rated)

5) Screws must be 15 mm (0.59 in) longer than the standard flange screws

6) ECTFE coating on AISI 316/316L. When using in hazardous areas, avoid electrostatic charging of the plastic surfaces.

7) MWP 10 bar (150 psi), OPL max. 15 bar (225 psi); process temperature range: -10 to +60 °C (+14 to +140 °F)

## JIS flanges, connection dimensions in accordance with JIS B 2220 BL, raised face RF




Flange	Flange Bo								Weight 1)	Option <sup>2)</sup>
Material	Nominal diameter	Nominal pressure	D b g	g	Quantity	<b>g</b> <sub>2</sub>	k			
			mm	mm	mm		mm	mm	kg (lb)	
	50 A	10 K	155	16	96	4	19	120	2.9 (6.39)	KF
AISI 316L (1.4435)	80 A	10 K	185	18	127	8	19	150	3.9 (8.60)	KL.
, , , ,	100 A	10 K	210	18	151	8	19	175	5.3 (11.69)	KH

1) Total weight consisting of the sensor assembly and the process connection.

#### Process connections for PMC71 with flush membrane

# China standard flanges, connection dimensions HG/T 20592-2009 (DN-flanges) or HG/T 20615-2009 ("-flanges), raised face RF




Flange <sup>1)</sup>	lange <sup>1)</sup>								Weight	Option <sup>2)</sup>
Nominal diameter	Class/ nominal pressure	D b g		g	g m	Quantity	<b>g</b> <sub>2</sub>	k		
		[mm]	[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]	
DN										,
DN50	40 bar	165	20	102	27.5	4	18	125	3 (6.6)	7H
DN80	40 bar	200	24	138	45.5	8	18	160	5.5 (12.13)	7K
[in]										
2"	150lb./sq.in	150	17.5	92.1	22.55	4	18	120.7	2.2 (4.85)	7P
2"	300 lb./sq.in	165	20.7	92.1	22.55	8	18	127	3 (6.62)	7R
3"	150 lb./sq.in	190	22.3	127	40	4	18	152.4	4.7 (10.36)	7V
3"	300 lb./sq.in	210	27	127	40	8	22	168.3	6.6 (14.55)	7X

1) Material: AISI 316L

# PMC71 hygiene

# Hygienic process connections with flush membrane

Many process connections with an EPDM or HNBR seal are approved for the PMC71 in accordance with the guidelines of the 3A Sanitary Standard. To ensure the 3A approval for the PMC71 version is valid, a 3A-approved process connection must be selected in combination with an EPDM or HNBR seal when ordering (Product Configurator, order code for "Seal", option B or F).



Item	Designation	Nominal pressure	Material <sup>1)</sup>	Weight	Approval <sup>2)</sup>	Option <sup>3)</sup>
				kg (lb) <sup>4)</sup>	-	
А	DIN 11851 DN 40, with HNBR or EPDM seal	PN 25		1.3(2.87)	EHEDG, 3A, CRN	MP <sup>5)</sup>
В	DIN 11851 DN 50, with HNBR or EPDM seal	PN 25		1.27 (2.80)	EHEDG, 3A, CRN	MR <sup>5)</sup>
С	Tri-Clamp ISO 2852 DN 38 (1 1/2"), DIN32676	PN 40 <sup>7)</sup>	AISI 316L (1.4435)	0.95 (2.09)	6)	TJ
D	Tri-Clamp ISO 2852 DN 51 (2"), with HNBR or EPDM seal	PN 40 <sup>7)</sup>		0.83 (1.83)	EHEDG, 3A, CRN	TD
E	Tri-Clamp ISO 2852 DN 76.1 (3"), with NBR or EPDM seal	PN 40 <sup>7)</sup>		1.2 (2.65)	EHEDG, 3A, CRN	TF

1) Delta ferrite content < 1 %. Roughness of wetted surfaces  $R_a < 0.76 \mu m$  (29.9  $\mu in$ ) as standard. Lower surface roughness on request.

2) CSA approval: Product Configurator, order code for "Approval"


3) Product Configurator, order code for "Process connection"

4) Total weight consisting of the sensor assembly and the process connection.

5) Endress+Hauser supplies these slotted nuts in stainless steel AISI 304 (DIN/EN material number 1.4301) or in AISI 304L (DIN/EN material number 1.4307).

6) See Section "Certificates and approvals"

7) Restricted nominal pressure (13.8 bar (200 psi)) for the following approvals: Product Configurator, order code for "Approval", option "E", "U" and "V".



Item	Designation	Nominal pressure	Material <sup>1)</sup>	Weight	Approval <sup>2)</sup>	Option <sup>3)</sup>
				kg (lb) <sup>4)</sup>		
F	DRD DN50 (65 mm) Slip-on flange with HNBR or EPDM seal	PN 25	AISI 316L	1.28 (2.82)	-	ТК
G	Varivent type N for pipes 40 – 162, with HNBR or EPDM seal	PN 40	(1.4435)	1.09 (2.40)	EHEDG, 3A, CRN	TR <sup>5)</sup>

1) Delta ferrite content < 1 %. Roughness of wetted surfaces  $R_a < 0.76 \mu m$  (29.9  $\mu in$ ) as standard. Lower surface roughness on request.

2) CSA approval: Product Configurator, order code for "Approval"


3) Product Configurator, order code for "Process connection"

4) Total weight consisting of the sensor assembly and the process connection.


5) Endress+Hauser supplies these slotted nuts in stainless steel AISI 304 (DIN/EN material number 1.4301) or in AISI 304L (DIN/EN material number 1.4307).

#### Process connections for PMP71 with internal process membrane

# Thread ISO 228 G



Item	Designation	Material	Weight	Option <sup>1)</sup>
			kg (lb)	
А	Thread ISO 228 G ½" A EN 837	AISI 316L	-	GA
		Alloy C276 (2.4819)		GB
D	Thread ISO 228 G ½" A,	AISI 316L		GE
В	G ¼" (female)	Alloy C276 (2.4819)	0.63 (1.39)	GF
С	Thread ISO 228 G ½" A,	AISI 316L		GH
	Bore 11.4 mm (0.45 in)	Alloy C276 (2.4819)		GJ




Item	Designation	Material	Weight	Approval <sup>1)</sup>	Option <sup>2)</sup>
			kg (lb)		
A	ANSI ½" MNPT, ¼" FNPT	AISI 316L		CRN	RA
A	AINSI 72 IVIINE 1, 74 I'INE I	Alloy C276 (2.4819)	0.63 (1.39)	CRN	RB
В	ANSI ½" MNPT, Bore 11.4 mm (0.45 in) = 400 bar (6000 psi) Bore 3.2 mm (0.13 in) = 700 bar (10500 psi)	AISI 316L		CRN	RD
		Alloy C276 (2.4819)		CRN	RE
С	ANSI 1/2" FNPT	AISI 316L	- 0.7 (1.54)	CRN	RH
		Alloy C276 (2.4819)		CRN	RJ

1) CSA approval: Product Configurator, order code for "Approval"

#### Process connections for PMP71 with internal process membrane

Thread JIS



Item Designation Material


ltem	Designation	Material	Weight	Option "
			kg (lb)	
А	JIS B0202 G ½" (male)	AISI 316L	0.6 (1.32)	GL
В	JIS B0203 R ½" (male)	AISI 510L	0.0 (1.52)	RL

.....

1)

1) Product Configurator, order code for "Process connection"


# Thread DIN 13




Item	Designation	Material	Weight	Option <sup>1)</sup>
			kg (lb)	
А	DIN 13 M20 x 1.5 11.4 mm (0.45 in)	AISI 316L		GP
		Alloy C276 (2.4819)	0.6 (1.32)	GQ
В	DIN 13 M20 x 1.5, EN 837 3 mm (0.12 in)	AISI 316L	0.0 (1.52)	GR
		Alloy C276 (2.4819)		GS

#### Process connections for PMP71 with flush membrane


Thread ISO 228 G



Item	Designation	Material	Weight	Option <sup>1)</sup>
			kg (lb)	
^	Thread ISO 228 G ½" A, DIN 3852 FKM form seal (item 1) pre-installed	AISI 316L	0.4 (0.88)	1A
A		Alloy C276 (2.4819)	0.4 (0.88)	1B
В	Thread ISO 228 G 1" A	AISI 316L	0.7 (1.54)	1D
		Alloy C276 (2.4819)		1E
С	Thread ISO 228 G 1 ½" A	AISI 316L	1.1 (2.43)	1G
		Alloy C276 (2.4819)		1H
D	Thread ISO 228 G 2" A	AISI 316L	1.5 (3.31)	1K
	read ISO 228 G Z" A	Alloy C276 (2.4819)	1	1L



Item	Designation	Material	Weight	Option <sup>1)</sup>
			kg (lb)	
	Thread DIN 16288 M20 x 1.5	AISI 316L	- 0.4 (0.88)	1N
A	FKM 80 flat seal (item 1) pre-installed	Alloy C276 (2.4819)		1P
В	Thread DIN 13 M44 x 1.25	AISI 316L	- 1.1 (2.43)	1R
		Alloy C276 (2.4819)		1S




Item	Designation	Material	Weight	Approval <sup>1)</sup>	Option <sup>2)</sup>
			kg (lb)	-	
	ANSI 1" MNPT	AISI 316L	0.7 (1.54)	CRN	2A
A	AINSET IVIINPT	Alloy C276 (2.4819)	0.7 (1.54)	CRN	2B
в	ANSI 1 ½" MNPT	AISI 316L	1 (2.21)	CRN	2D
D		Alloy C276 (2.4819)		CRN	2E
С	ANSI 2" MNPT	AISI 316L	1.3 (2.87)	CRN	2G
		Alloy C276 (2.4819)		CRN	2Н

CSA approval: Product Configurator, order code for "Approval" Product Configurator, order code for "Process connection" 1) 2)


Process connections for PMP71 with flush membrane

EN flanges, connection dimensions in accordance with EN 1092-1



Flange <sup>1)</sup>	ange <sup>1)</sup>						Boltholes			Weight	Option <sup>2)</sup>
Nominal	Nominal	Form	ØD	c <sub>4</sub>	Ød <sub>1</sub>	f <sub>1</sub>	Quantity	ØL	Øk	Flange	
diameter	pressure		mm	mm	mm	mm	-	mm	mm	kg (lb)	
DN 25	PN 10-40	B1	115	18	68	2	4	14	85	1.38 (3.04)	CN
DN 32	PN 10-40	B1	140	18	78	2	4	18	100	2.03 (4.48)	СР
DN 40	PN 10-40	B1	150	18	88	3	4	18	110	2.35 (5.18)	CQ
DN 50	PN 10-40	B1	165	20	102	3	4	18	125	3.2 (7.06)	В3
DN 80	PN 10-40	B1	200	24	138	3	8	18	160	5.54 (12.22)	B4

1) Material: AISI 316L




Flange <sup>1)</sup>						Bo	ltholes		Weight	Approval <sup>2)</sup>	Option <sup>3)</sup>
Nominal diameter	Class/ nominal pressure	D	b	g	с	Q	<b>g</b> <sub>2</sub>	k			
[in]	lb./sq.in	[in]	[in]	[in]	[in]		[in]	[in]	[kg]		
1	150	4.25	0.61	2.44	0.08	4	0.62	3.13	1.1 (2.43)	CRN	AA
1	300	4.88	0.69	2.70	0.06	4	0.75	3.5	1.3 (2.87)	CRN	AN
1 1/2	150	5	0.69	2.88	0.08	4	0.62	3.88	1.5 (3.31)	CRN	AE
1 1/2	300	6.12	0.81	2.88	0.08	4	0.88	4.5	2.6 (5.73)	CRN	AQ
2	150	6	0.75	3.62	0.08	4	0.75	4.75	2.4 (5.29)	CRN	AF
2	300	6.5	0.88	3.62	0.08	8	0.75	5	3.2 (7.06)	CRN	AR
3	150	7.5	0.94	5	0.08	4	0.75	6	4.9 (10.8)	CRN	AG
3	300	8.25	1.12	5	0.08	8	0.88	6.62	6.7 (14.77)	CRN	AS
4	150	9	0.94	6.19	0.08	8	0.75	7.5	7.1 (15.66)	CRN	AH
4	300	10	1.25	6.19	0.08	8	0.88	7.88	11.6 (25.88)	CRN	AT

1) Material: AISI 316/316L; Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual rated)

2) CSA approval: Product Configurator order code for "Approval"

Process connections for PMP71 with flush-mounted process isolating diaphragm




JIS flanges, connection dimensions in accordance with JIS B 2220 BL, raised face RF

- Diameter of flange Thickness D
- b
- Raised face g
- k Hole circle
- $g_2$ Diameter of hole
- Engineering unit mm

Flange				Boltholes			Weight	Option <sup>1)</sup>		
Material	Nominal diameter	Class/	D	b	g	Number	<b>g</b> <sub>2</sub>	k	Flange	
		Nominal pressure	[mm]	[mm]	[mm]		[mm]	[mm]	[kg]	
AISI 316L	25 A	20 K	125	16	67	4	19	90	1.5 (3.31)	KA
AISI 316L	50 A	10 K	155	16	96	4	19	120	2.0 (4.41)	CF
AISI 316L	80 A	10 K	185	18	127	8	19	150	3.3 (7.28)	KL
AISI 316L	100 A	10 K	210	18	151	8	19	175	4.4 (9.7)	KH

PMP71: process connections with flush-mounted process isolating diaphragm

# China standard flanges, connection dimensions HG/T 20592-2009 (DN-flanges) or HG/T 20615-2009 ("-flanges), raised face RF $\,$




Flange <sup>1)</sup>	ange 1)								Weight	Option <sup>2)</sup>
Nominal diameter	Class/nominal pressure	D	b	g	m	Number	<b>g</b> <sub>2</sub>	k		
		[mm]	[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]	1
DN									•	
DN50	40 bar	165	20	102	27.5	4	18	125	3 (6.6)	7H
DN80	40 bar	200	24	138	45.5	8	18	160	5.5 (12.13)	7K
[in]									•	
2"	150lb./sq.in	150	17.5	92.1	22.55	4	18	120.7	2.2 (4.85)	7P
2"	300 lb./sq.in	165	20.7	92.1	22.55	8	18	127	3 (6.62)	7R
3"	150 lb./sq.in	190	22.3	127	40	4	18	152.4	4.7 (10.36)	7V
3"	300 lb./sq.in	210	27	127	40	8	22	168.3	6.6 (14.55)	7X

1) Material: AISI 316L

#### Process connections for PMP71






Material	Designation	Weight	Approval <sup>1)</sup>	Option <sup>2)</sup>
		kg (lb)		
AISI 316L (1.4404)	Oval flange adapter 1/4-18 NPT as per IEC 61518 Mounting: 7/16-20 UNF	1.9 (4.19)	CRN	UR

1) CSA approval: Product Configurator, order code for "Approval"

2) Product Configurator, order code for "Process connection"

Process connections for PMP71

### Prepared for diaphragm seal mount




Material	Description	Weight in kg (lb)	Approval <sup>1)</sup>	Option <sup>2)</sup>
AISI 316L (1.4404)	Prepared for diaphragm seal mount	1.9 (4.19)	CRN	U1

1) CSA approval: Product Configurator, order code for "Approval"

# Valve manifold DA63M- En (optional) fol

Endress+Hauser supplies milled valve manifolds via the transmitter's product structure in the following versions:




- 2-way valve manifolds in 316L or AlloyC can be
- ordered as an **enclosed** accessory (seal for mounting is enclosed)
- ordered as a **mounted** accessory (mounted valve manifolds are supplied with a documented leakage test).

Certificates ordered with the equipment (e.g. 3.1 material certificate and NACE) and tests (e.g. PMI and pressure test) apply to the transmitter and the valve manifold.

For other details (order option, dimension, weight, materials), see SD01553P/00/EN "Mechanical accessories for pressure measuring devices".

During the operating life of the valves, it may be necessary to re-tighten the packing.


## Mounting on valve manifold



Ordering information:

Product Configurator, order code for "Accessories mounted"


## PMP75 basic device



Process connections for PMP75 with flush membrane

- The weights of the diaphragm seals are given in the tables. For weight of housing, see  $\rightarrow \cong 53$ 
  - The following drawings are schematic diagrams. In other words, the dimensions of a diaphragm seal supplied may deviate from the dimensions specified in this document.
  - Observe the information in the "Planning instructions for diaphragm seal systems" section
     → 
     <sup>1</sup>→ 
     <sup>1</sup>17
  - For further information please contact your local Endress+Hauser Sales Center.

### Pancake seal



Flange					Diaphragm seal	Approval <sup>1)</sup>	Option <sup>2)</sup>
Material	Nominal diameter	Nominal pressure <sup>3)</sup>	D	b	Weight		
			[mm]	[mm]	[kg (lb)]		
	DN 50	PN 16-400	102	20 - 22	1.3 (2.87)	-	UI <sup>4)</sup>
	DN 80	PN 16-400	138	20 - 22	2.3 (5.07)	-	UJ <sup>4)</sup>
	DN 100	PN 16-400	162	20 - 22	3.1 (6.84)	-	UK
AISI 316L	[in]	[lb/sq.in]	[in]	[in]			
	2	150-2500	3.89	0.79 - 0.87	1.3 (2.87)	CRN	UL 4)
	3	150-2500	5.00	0.79 - 0.87	2.3 (5.07)	CRN	UM 4)
	4	150-2500	6.22	0.79 - 0.87	3.1 (6.84)	CRN	UR

1) CSA approval: Product Configurator, order code for "Approval"

2) Product Configurator, order code for "Process connection"


3) The specified nominal pressure applies to the diaphragm seal. The maximum pressure for the measuring device is dependent on the lowest-rated element, with regard to pressure, of the selected components  $\rightarrow \cong 51$ .

4) With TempC Membrane

### Maximum diameter of membrane $Ød_M$

DN	PN			Ød <sub>M</sub> (n	nm)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
50	16-400	61	58	62	60	59	52
80	16-400	89	89	90	92	89	80
100	16-400	-	89	90	92	89	-

NPS	Class			Ød <sub>M</sub> (	in)		
in		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
2	150-2500	2.40	2.05	2.32	2.36	2.32	2.05
3	150-2500	3.50	3.50	3.54	3.62	3.50	3.14
4	150-2500	-	3.14	3.50	3.62	3.50	-




Thread							Diaphr	agm seal		Approval <sup>1)</sup>	Option <sup>2)</sup>
Material	G	Nominal pressure	d1	d <sub>2</sub>	<b>x</b> 1	SW/AF	d <sub>M</sub>	h	Weight		
		PN	[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]		
AISI 316L	G 1" A	400	30	39	21 3)	32	30	19	0.4 (0.88)	-	1D
Alloy C276									0.5 (1.1)	-	1E
AISI 316L	G 1 ½" A	400	44	55	30	50	42	20	0.9 (1.98)	-	1G
Alloy C276									1.0 (2.21)	-	1H
AISI 316L	G 2"	400	56	68	30	65	50	20	1.9 (4.19)	-	1K
Alloy C276									2.1 (4.63)	-	1L
AISI 316L	1" MNPT	400	-	45	28	41	24	17	0.6 (1.32)	CRN	2A
Alloy C276	-								0.7 (1.54)	CRN	2B
AISI 316L	1 ½" MNPT	400	-	60	30	41	36	20	0.9 (1.98)	CRN	2D
Alloy C276	-			52	30	46	32	20	1.0 (2.21)	CRN	2E
AISI 316L	2" MNPT	400	-	78	30	65	38	25	1.8 (3.97)	CRN	2G
Alloy C276									2.0 (4.41)	CRN	2H


1) CSA approval: Product Configurator, order code for "Approval"

2) Product Configurator, order code for "Process connection"

3) 28 mm (1.1 in) in conjunction with high-temperature oil

PMP75: Process connections with flush TempC membrane





Thread					Diaphra	gm seal		Approval <sup>1)</sup>	Option <sup>2)</sup>		
Material	G	Nominal pressure	d1	d <sub>2</sub>	x1	AF	d <sub>M</sub>	h	Weight		
		PN	[mm]	[mm]	[mm]	1	[mm]	[mm]	[kg (lb)]		
AISI 316L	G 1" A	400	30	39	21	41	28	19	0.35 (0.77)	-	1D
Alloy C276	]								0.38 (0.84)	-	1E
AISI 316L	G 1 ½" A	400	-	55	30	46	41	20	0.73 (1.61)	-	1G
Alloy C276	]								0.79 (1.74)	-	1H
AISI 316L	G 2"	400	-	68	30	60	48	20	1.20 (2.65)	-	1K
Alloy C276	1								1.30 (2.87)	-	1L

1) CSA approval: Product Configurator, order code for "Approval"


2) Product Configurator, order code for "Process connection"

Thread				Diaphra	ıgm seal		Approval <sup>1)</sup>	Option <sup>2)</sup>			
Material	MNPT	Nominal pressure	d1	d <sub>2</sub>	<b>x</b> <sub>1</sub>	AF	d <sub>M</sub>	h	Weight		
		PN	[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]		
AISI 316L	1" MNPT	400	-	45	23	41	28	16	0.38 (0.84)	CRN	2A
Alloy C276									0.41 (0,90)	CRN	2B
AISI 316L	1 ½" MNPT	400	-	60	30	46	41	20	0.70 (1.54)	CRN	2D
Alloy C276									0.76 (1.68)	CRN	2E
AISI 316L	2" MNPT	400	-	60	34	46	48	21	1.10 (2.43)	CRN	2G
Alloy C276									1.19 (2.62)	CRN	2H

1) CSA approval: Product Configurator, order code for "Approval"

Process connections for PMP75 with flush-mounted process isolating diaphragm

## Tri-Clamp ISO 2852



Material 1)	Nominal	Nominal	Nominal	C <sub>7</sub>	d <sub>M</sub>		h	Weight	Approval <sup>2)</sup>	Option <sup>3)</sup>
	diameter ISO 2852	diameter DIN 32676	diameter		Standard	with TempC Membrane				
			[in]	[mm]	[mm]	[mm]	[mm]	[kg (lb)]		
	ND 25 / 33.7	DN 25	1	50.5	24	-	37	0.32 (0.71)	EHEDG, 3A, CRN	ТВ
	ND 38	DN 40	1 1/2	50.5	36	36	30	1 (2.21)	EHEDG, 3A, CRN	TC <sup>4) 5)</sup>
AISI 316L	ND 51 / 40	DN 50	2	64	48	41	30	1.1 (2.43)	EHEDG, 3A, CRN	TD <sup>4) 5)</sup>
	ND 63.5	DN 50	2 1/2	77.5	61	61	30	0.7 (1.54)	EHEDG, 3A	TE <sup>6)</sup>
	ND 76.1	-	3	91	73	61	30	1.2 (2.65)	EHEDG, 3A, CRN	TF <sup>5)</sup>

1) Surface roughness of the wetted surfaces  $R_a < 0.76 \mu m$  (29.9  $\mu in$ ) as standard. Lower surface roughness available on request.

2) CSA approval: Product Configurator, order code for "Approval"

3) Product Configurator, order code for "Process connection"


4) Optionally available as an ASME-BPE-compliant diaphragm seal version for use in biochemical processes, surfaces in contact with medium  $R_a < 0.38 \ \mu m (15 \ \mu in))$ , electropolished; order using order code for "Additional options", option "P".


5) Alternatively available with TempC Membrane.

6) With TempC Membrane

PN max. = 40 bar (580 psi). The maximum PN depends on the clamp used.

Process connections for PMP75 with flush-mounted process isolating diaphragm





Material <sup>1)</sup>	Nominal diameter ISO 2852	Nominal diameter	Nominal pressure	D	d <sub>2</sub>	d <sub>3</sub>	h	L	Weight	Approval <sup>2)</sup>	Option <sup>3)</sup>
		[in]		[mm]	[mm]	[mm]	[mm]	[mm]	[kg (lb)]		
	DN 25	1	PN 40	22.5	50.5	54	67	126	1.7 (3.75)	3A, CRN	SB
AISI 316L	DN 38	1 1/2	PN 40	35.5	50.5	69	67	126	1.0 (2.21)	3A, CRN	SC <sup>4)</sup>
	DN 51	2	PN 40	48.6	64	78	79	100	1.7 (3.75)	3A, CRN	SD <sup>4)</sup>


1) Surface roughness of the wetted surfaces  $R_a < 0.76~\mu m$  (29.9  $\mu in)$  as standard.

2) CSA approval: Product Configurator, order code for "Approval"

3) Product Configurator, order code for "Process connection"

4) incl. 3.1 and pressure test according to Pressure Equipment Directive, Category II

Hygienic process connections Varivent for pipes for PMP75 with flush mount process isolating diaphragm



Material <sup>1)</sup>	Designation	Nominal pressure	D	d <sub>M</sub>		Weight	Approval	Option <sup>2)</sup>
				Standard	With TempC Membrane			
			[mm]	[mm]	[mm]	[kg (lb)]		
AISI 316L	Type F for pipes DN 25 - DN 32	PN 40	50	34	36	0.4 (0.88)	EHEDG, 3A	TU <sup>3)</sup>
AISI 316L	Type N for pipes DN 40 - DN 162	PN 40	68	58	61	0.8 (1.76)	EHEDG, 3A	TR <sup>4) 5)</sup>

1) Surface roughness of the surfaces in contact with the medium  $R_a < 0.76 \ \mu m$  (29.9  $\mu in$ ) as standard.


2) Product Configurator, order code for "Process connection"

3) With TempC Membrane

4) Optionally available as an ASME-BPE-compliant diaphragm seal version for use in biochemical processes, surfaces in contact with medium R<sub>a</sub> <

0.38 μm (15 μin)), electropolished; order using order code for "Additional options", option "P". Lower surface roughness on request.

5) Alternatively available with TempC Membrane.



### DRD DN50 (65 mm)

Material <sup>1)</sup>	Nominal pressure	d <sub>M</sub>		Weight	Option <sup>2)</sup>
		Standard	With TempC Membrane		
		[mm]	[mm]	[kg (lb)]	
AISI 316L	PN 25	50	48	0.75 (1.65)	TK <sup>3) 4)</sup>

1) Surface roughness of the wetted surfaces  $R_a < 0.76~\mu m$  (29.9  $\mu in)$  as standard.


2) Product Configurator, order code for "Process connection"

3) Alternatively available with TempC Membrane.

<sup>4)</sup> Including slip-on flange.

Hygienic process connections for PMP75 with flushmounted process isolating diaphragm

## SMS nozzles with coupling nut




Material 1)	Nominal diameter	Nominal pressure	D	f	G	m	h	d <sub>M</sub>	Weight	Approval	Option <sup>2)</sup>
			[mm]	[mm]		[mm]	[mm]	[mm]	[kg (lb)]		
	1	PN 25	54	3.5	Rd 40 - 1/6	20	42.5	24	0.25 (0.55)	3A	TG
AISI 316L	1 1/2	PN 25	74	4	Rd 60 - 1/6	25	57	36	0.65 (1.43)	3A	TH <sup>3)</sup>
	2	PN 25	84	4	Rd 70 - 1/6	26	62	48	1.05 (2.32)	3A	TI <sup>3)</sup>

1) Surface roughness of the wetted surfaces  $R_a$  < 0.76  $\mu m$  (29.9  $\mu in)$  as standard.

2) Product Configurator, order code for "Process connection"

3) Alternatively available with TempC Membrane.

### APV-RJT nozzles with coupling nut




Material <sup>1)</sup>	Nominal diameter	Nominal pressure	D	f	G	m	h	d <sub>M</sub>	Weight	Option <sup>2)</sup>
	[in]	[bar]	[mm]	[mm]		[mm]	[mm]	[mm]	[kg (lb)]	
	1	PN 40	77	6.5	1 13/16 - 1/8"	22	42.6	21	0.45 (0.99)	TL
AISI 316L	1 1/2	PN 40	72	6.4	2 5/16 - 1/8"	22	42.6	28	0.75 (1.65)	ТМ
	2	PN 40	86	6.4	2 7/8 - 1/8"	22	42.6	38	1.2 (2.65)	TN

1) Surface roughness of the wetted surfaces  $R_a < 0.76~\mu m$  (29.9  $\mu in)$  as standard.

2) Product Configurator, order code for "Process connection"

### APV-ISS nozzles with coupling nut




Material <sup>1)</sup>	Nominal diameter	Nominal pressure	D	G	SW/AF	d <sub>M</sub>	Weight	Option <sup>2)</sup>
	[in]	[bar]	[mm]			[mm]	[kg (lb)]	
	1	PN 40	54.1	1 1/2" - 1/8"	46.8	24	0.4 (0.88)	TP
AISI 316L	1 1/2	PN 40	72	2" - 1/8"	62	34	0.6 (1.32)	TQ
	2	PN 40	89	2 1⁄2" - 1/8"	77	45	1.1 (2.43)	TS

1) Surface roughness of the wetted surfaces  $R_a < 0.76~\mu m$  (29.9  $\mu in)$  as standard.

Hygienic process connections for PMP75 with flush membrane

## Taper adapter with slotted nut, DIN 11851



Material <sup>1)</sup>	Taper adapte	er			Slotted nut		Diaphrag	n seal		Approval	Option <sup>2)</sup>
							d <sub>M</sub>		Weight		
	Designation	pressure [bar] [mm] [mm]			G	m	Standard With TempC Membrane				
		[bar]	[mm]	[mm]		[mm]	[mm]	[mm]	[kg (lb)]		
	DN 32	PN 40	50	10	Rd 58 x 1/6"	21	32	28	0.45 (0.99)	3A, EHEDG	MI <sup>3)</sup>
	DN 40	PN 40	56	10	Rd 65 x 1/6"	21	38	36	0.45 (0.99)	3A, EHEDG	MZ <sup>3)</sup>
AISI 316L	DN 50	PN 25	68.5	11	Rd 78 x 1/6"	19	52	48	1.1 (2.43)	3A, EHEDG	MR <sup>4)</sup>
	DN 65	PN 25	86	12	Rd 95 x 1/6"	21	66	61	2.0 (4.41)	3A, EHEDG	MS <sup>4)</sup>
	DN 80	PN 25	100	12	Rd 110 x 1/4"	26	81	61	2.55 (5.62)	3A, EHEDG	MT <sup>4)</sup>


1) Roughness of wetted surfaces  $R_a$  < 0.76  $\mu m$  (29.9  $\mu in)$  as standard.

2) Product Configurator, order code for "Process connection"

3) With TempC Membrane

4) Alternatively available with TempC Membrane.

### NEUMO BioControl



Material <sup>1)</sup>	NEUMO Bio	Control <sup>2)</sup>							Diaphrag	m seal		Approval	Option <sup>3)</sup>
									d <sub>M</sub>		Weight		
	Nominal diameter	Nominal pressure	D	d	d <sub>2</sub>	d <sub>3</sub>	d <sub>1</sub>	m	Standard	With TempC Membrane			
		[bar]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[kg (lb)]		
	DN 50	PN 16	90	17	4 x Ø 9	50	70	27	40	36	1.1 (2.43)	3A	S4 <sup>4)</sup>
AISI 316L	DN 80	PN 16	140	25	4 x Ø 11	87.4	115	37	61	61	2.6 (5.73)	3A	S6 <sup>4)</sup>


1) Roughness of wetted surfaces  $R_a < 0.76~\mu m$  (29.9  $\mu in)$  as standard.

2) (process temperature range: -10 to +200 °C (+14 to +392 °F))

Product Configurator, order code for "Process connection"

4) With TempC Membrane

### Universal process adapter




- The roughness of the surface in contact with the medium  $R_a < 0.76~\mu m$  (30  $\mu in)$
- Temperature operating range: -60 to +150 °C (-76 to +302 °F)
- Silicone molded seal: FDA 21CFR177.2600/USP Class VI, order number: 52023572

Designation	Nominal pressure	Weight	Approval	Option <sup>1)</sup>
	bar (psi)	[kg (lb)]		
Universal process adapter Molded seal made of silicone (4)	10	0.8 (1.76)	3A	00 <sup>2)</sup>

1) Product Configurator, "Process connection" ordering feature

2) Alternatively available with TempC Membrane.



Flange <sup>1) 2) 3)</sup>							Boltholes			Diaphragm seal	Option <sup>4)</sup>
Nominal diameter	Nominal pressure	Туре	ØD	c <sub>4</sub>	Ød <sub>1</sub>	f <sub>1</sub>	Number	ØL	Øk	Weight	
			mm	mm	mm	mm	1	mm	mm	kg (lb)	
DN 25	PN 10-40	B1	115	18	68	2	4	14	85	1.38 (3.04)	CN <sup>5) 6)</sup>
DN 25	PN 63-160	B2	140	24	68	2	4	18	100	2.54 (5.60)	DN
DN 25	PN 250	B2	150	28	68	2	4	22	105	3.7 (8.16)	EN
DN 25	PN 400	B2	180	38	68	2	4	26	130	6.65 (14.66)	E1
DN 32	PN 10-40	B1	140	18	78	2	4	18	100	2.03 (4.48)	СР
DN 40	PN 10-40	B1	150	18	88	3	4	18	110	2.35 (5.18)	CQ
DN 50	PN 10-40	B1	165	20	102	3	4	18	125	3.2 (7.06)	B3 <sup>5) 6)</sup>
DN 50	PN 63	B2	180	26	102	3	4	22	135	4.52 (9.97)	С3
DN 50	PN 100-160	B2	195	30	102	3	4	26	145	6.07 (13.38)	EF
DN 50	PN 250	B2	200	38	102	3	8	26	150	7.7 (16.98)	ER
DN 50	PN 400	B2	235	52	102	3	8	30	180	14.7 (32.41)	E3
DN 80	PN 10-40	B1	200	24	138	3	8	18	160	5.54 (12.22)	B4 <sup>5) 6)</sup>
DN 80	PN 100	B2	230	32	138	3	8	26	180	8.85 (19.51)	C4
DN 100	PN 100	B2	265	36	162	3	8	30	210	13.3 (29.33)	C5

1) Material: AISI 316L

2) The roughness of the surface in contact with the medium including the raised face of the flanges (all standards) made of Alloy C276, Monel, tantalum, gold > 316L or PTFE is  $R_a < 0.8 \ \mu m$  (31.5  $\mu in$ ). Reduced surface roughness available on request.

3) The raised face of the flange is made of the same material as the process membrane.


4) Product Configurator, order code for "Process connection"

5) Alternatively available with TempC membrane. Change in diameter of process membrane in TempC version: DN25: 28 mm; DN50: 61 mm.

6) Alternatively available with gold-coated TempC membrane (Product Configurator, order code for "Membrane material" option "G").

DN	PN			Ød <sub>M</sub> (r	nm)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
DN 25	PN 10-40	28	29.6	33	33	33	28
DN 25	PN 63-160	-	28	28	28	28	-
DN 25	PN 250	-	28	28	28	28	-
DN 25	PN 400	-	28	28	28	28	-
DN 32	PN 10-40	-	34	42	42	34	-
DN 40	PN 10-40	-	38	48	51	42	-
DN 50	PN 10-40	61	58	57	60	59	52
DN 50	PN 63	-	52	62	60	59	-
DN 50	PN 100-160	-	52	62	60	59	-
DN 50	250	-	52	62	60	59	-
DN 50	400	-	52	62	60	59	-
DN 80	PN 10-40	89	89	89	92	89	80
DN 80	PN 100	-	80	90	92	90	-
DN 100	PN 100	-	80	90	92	89	-

## Maximum diameter of membrane $\mathcal{O}d_M$



EN flanges with barrel (extended diaphragm seal), connection dimensions in accordance with EN 1092-1  $\,$ 

Flange <sup>1) 2)</sup>	Flange <sup>1) 2)</sup>								Diaphra	Diaphragm seal		
Nominal diameterNominal pressureTypeØDc4ØD				Ød <sub>1</sub>	Number	ØL	Øk	d <sub>M</sub>	Weight			
			mm	mm	mm		mm	mm	mm	kg (lb)		
DN 50	PN 10-40	B1	165	20	102	4	18	125	48	4)	D3 <sup>4)</sup>	
DN 80	PN 10-40	B1	200	24	138	8	18	160	73	4)	D4 <sup>4)</sup>	

1) Material: AISI 316L

2) In the case of process membranes made of Alloy C276, Monel or tantalum, the raised face of the flange and the barrel pipe are made of 316L


3) Product Configurator, order code for "Process connection"

4) Available with 50 mm (1.97 in), 100 mm (3.94 in) and 200 mm (7.87 in)barrel (extended diaphragm seal), for barrel diameter and weight see the following table

Option <sup>1)</sup>	Nominal diameter	Nominal pressure	L	d <sub>3</sub>	Weight
			[mm]	[mm]	[kg (lb)]
D3	DN 50	PN 10-40	50 / 100 / 200	48.3	3.44 (7.59) / 3.8 (8.4) / 4.1 (9.04) / 4.4 (9.7)
D4	DN 80	PN 10-40	50 / 100 / 200	76	6.2 (13.7) / 6.7 (14.8) / 7.27 (16.03) / 7.8 (17.2)

Process connections for PMP75 with flush membrane

ASME flanges, connection dimensions as per ASME B 16.5, raised face RF



Flange <sup>1) 2) 3)</sup>						Boltholes			Diaphragm seal	4) 5)	Option <sup>6)</sup>
Nominal diameter	Class	D	b	g	f	Number	<b>g</b> <sub>2</sub>	k	Weight		
[in]	[lb./sq.in]	[in]	[in]	[in]	[in]		[in]	[in]	[kg (lb)]		
1	150	4.25	0.56	2	0.08	4	0.62	3.12	1.2 (2.65)	CRN <sup>7)</sup>	AC <sup>8)9)</sup>
1	300	4.88	0.69	2	0.08	4	0.75	3.5	1.3 (2.87)	CRN	AN <sup>8) 9)</sup>
1	400/600	4.88	0.69	2	0.25	4	0.75	3.5	1.4 (3.09)	CRN	HC
1	900/1500	5.88	1.12	2	0.25	4	1	4	3.2 (7.06)	CRN	HN
1	2500	6.25	1.38	2	0.25	4	1	4.25	4.6 (10.14)	CRN	НО
1 1/2	150	5	0.69	2.88	0.06	4	0.62	3.88	1.5 (3.31)	CRN	AE
1 1/2	300	6.12	0.81	2.88	0.06	4	0.88	4.5	2.6 (5.73)	CRN	AQ
2	150	6	0.75	3.62	0.06	4	0.75	4.75	2.2 (4.85)	CRN	AF 8) 9)
2	300	6.5	0.88	3.62	0.06	8	0.75	5	3.4 (7.5)	CRN	AR <sup>8)9)</sup>
2	400/600	6.5	1	3.62	0.25	8	0.75	5	4.3 (9.48)	CRN	HF
2	900/1500	8.5	1.5	3.62	0.25	8	1	6.5	10.3 (22.71)	CRN	HR
2	2500	9.25	2	3.62	0.25	8	1.12	6.75	15.8 (34.84)	-	Н3
3	150	7.5	0.94	5	0.06	4	0.75	6	5.1 (11.25)	CRN	AG <sup>8) 9)</sup>
3	300	8.25	1.12	5	0.06	8	0.75	6	7.0 (15.44)	CRN	AS <sup>8) 9)</sup>
4	150	9	0.94	6.19	0.06	8	0.75	7.5	7.2 (15.88)	CRN	AH
4	300	10	1.25	6.19	0.06	8	0.88	7.88	11.7 (25.8)	CRN	AT

1) Material AISI 316/316L: Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual-rated)

 The roughness of the surface in contact with the medium, including the raised face of the flanges (all standards) made of Alloy C276, Monel, tantalum, gold or PTFE, is R<sub>a</sub>< 0.8 μm (31.5 μin). Reduced surface roughness available on request.</li>

3) The raised face of the flange is made of the same material as the process membrane.

4) Approval

5) CSA approval: Product Configurator, order code for "Approval"

6) Product Configurator, order code for "Process connection"


7) CRN approval not for TempC membrane.

8) Alternatively available with TempC membrane. Change in diameter of process membrane in TempC version: nominal diameter 1": 1.1 in; 2": 2.40 in.

9) Alternatively available with gold-coated TempC membrane (Product Configurator, order code for "Membrane material" option "G").

NPS	Class			Ød <sub>M</sub> (in)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)
1	150	1.10	-	1.30	1.34	1.30
1	300	1.10	-	1.30	1.34	1.30
1	400/600	-	1.10	1.30	1.34	1.30
1	900/1500	-	1.10	1.10	1.02	1.10
1	2500	-	1.10	1.30	1.34	1.30
1 1/2	150	-	1.50	1.89	2.01	1.89
1 ½	300	-	1.50	1.89	2.01	1.89
2	150	2.40	-	2.44	2.44	2.44
2	300	2.40	-	2.44	2.44	2.44
2	400/600	-	2.05	2.44	2.44	2.44
2	900/1500	-	2.05	2.44	2.44	2.44
2	2500	-	2.05	2.44	2.44	2.44
3	150	3.50	-	3.62	3.62	3.62
3	300	3.50	-	3.62	3.62	3.62
4	150	-	3.15	3.62	3.62	3.62
4	300	-	3.15	3.62	3.62	3.62

## Maximum diameter of membrane $Ød_M$



# ASME flanges with barrel (extended diaphragm seal), connection dimensions in accordance with ASME B 16.5, raised face RF

Flange <sup>1) 2)</sup>						Boltholes			Diaphra	agm seal	3) 4)	Option <sup>5)</sup>
Nominal diameter	Class	D	b	g	f	Number	<b>g</b> <sub>2</sub>	k	d <sub>M</sub>	Weight	]	
[in]	[lb./sq.in]	[in]	[in]	[in]	[in]	-	[in]	[in]	[in]	[kg (lb)]		
2	150	6	0.75	3.62	0.06	4	0.75	4.75	1.85	6)	CRN	J3 <sup>6)</sup>
3	150	7.5	0.94	5	0.06	4	0.75	6	2.83	6)	CRN	J4 <sup>6)</sup>
3	300	8.25	1.12	5	0.06	8	0.88	6.62	2.83	6)	CRN	J7 <sup>6)</sup>
4	150	9	0.94	6.19	0.06	8	0.75	7.5	3.5	6)	CRN	J5 <sup>6)</sup>
4	300	10	1.25	6.19	0.06	8	0.88	7.88	3.5	6)	CRN	J8 <sup>6)</sup>

1) Material: AISI 316/316L. Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual-rated)

2) In the case of process membranes made of Alloy C276, Monel or tantalum, the raised face of the flange and the barrel pipe are made of 316L.


3) Approval

4) CSA approval: Product Configurator, order code for "Approval"

5) Product Configurator, order code for "Process connection"

6) Choice of 2", 4", 6" or 8" barrel (extended diaphragm seal), for diameter and weight of barrel (extended diaphragm seal) see the following table

Option <sup>1)</sup>	Nominal diameter	Class	(L)	d <sub>3</sub>	Weight
	[in]	[lb./sq.in]	in (mm)	in (mm)	[kg (lb)]
J3	2	150	2 (50.8) / 4 (101.6) / 6 (152.4) / 8 (203.2)	1.9 (48.3)	3.0 (6.6)/ 3.4 (7.5)/ 3.9 (8.6)/ 4.4 (9.7)
J4	3	150	2 (50.8) / 4 (101.6) / 6 (152.4) / 8 (203.2)	2.99 (76)	6.0 (13.2) / 6.6 (14.5) / 7.1 (15.7) / 7.8 (17.2)
J7	3	300	2 (50.8) / 4 (101.6) / 6 (152.4) / 8 (203.2)	2.99 (76)	7.9 (17.4) / 8.5 (18.7) / 9.0 (19.9) / 9.6 (21.2)
J5	4	150	2 (50.8) / 4 (101.6) / 6 (152.4) / 8 (203.2)	3.7 (94)	8.6 (19) / 9.9 (21.8) / 11.2 (24.7) / 12.4 (27.3)
J8	4	300	2 (50.8) / 4 (101.6) / 6 (152.4) / 8 (203.2)	3.7 (94)	13.1 (28.9)/ 14.4 (31.6)/ 15.7 (34.6)/ 16.9 (37.3)



### JIS flanges, connection dimensions in accordance with JIS B 2220 BL, raised face RF

Flange <sup>1) 2) 3)</sup>	Flange <sup>1) 2) 3)</sup>								Diaphragm seal	Option <sup>4)</sup>
Nominal diameter	Nominal pressure	D	b	g	f	Number	Number g <sub>2</sub> k		Weight	
		[mm]	[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]	
25 A	10 K	125	14	67	1	4	19	90	1.5 (3.31)	КС
50 A	10 K	155	16	96	2	4	19	120	2.3 (5.07)	KF
80 A	10 K	185	18	127	2	8	19	150	3.3 (7.28)	KL
100 A	10 K	210	18	151	2	8	19	175	4.4 (9.7)	КН

1) Material: AISI 316L

2) The roughness of the surface in contact with the medium, including the raised face of the flanges (all standards) made of Alloy C276, Monel,

tantalum, gold or PTFE, is  $R_a^{}<0.8~\mu m$  (31.5  $\mu in$ ). Reduced surface roughness available on request.

3) The raised face of the flange is made of the same material as the process membrane.

4) Product Configurator, order code for "Process connection"


### Maximum diameter of membrane $Ød_M$

A 1)	K <sup>2)</sup>			Ød <sub>M</sub> (n	nm)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
25 A	10 K	-	28	-	-	-	-
40 A	10 K	-	38	-	-	-	-
50 A	10 K	-	52	62	60	59	-
80 A	10 K	-	80	-	-	-	-
100 A	10 K	-	80	-	-	-	-

1) Alphanumeric designation of the flange size.

2) Alphanumeric pressure rating of a component.

## Process connections for Welded separators PMP75




Item	Designation	Material	Measuring range	Nominal pressure	Approval	Weight	Option <sup>1)</sup>
			[bar (psi)]	-		[kg (lb)]	
А	Welded, ISO 228 G ½ A EN837				-		UA
В	Welded, ANSI ½ MNPT	AISI 316L	≤ 160 (2320)	PN 160	CRN <sup>2)</sup>	1.43 (3.15)	UB
С	Welded, thread DIN13 M20x1.5				-		UF


1) Product Configurator, order code for "Process connection"

2) CSA approval: Product Configurator, order code for "Approval"

### **Threaded separators**




Item	Designation	Material	Measuring range	Nominal pressure	Weight	Option 1)
			[bar (psi)]		[kg (lb)]	
А	Threaded, ½" NPT with FKM Viton seal -20 to +200 °C (-4 to +392 °F)	AISI 316L	≤ 250 (3625)	PN 250	4.75 (10.47)	UG
В	Threaded, 1" NPT with FKM Viton seal $-20$ to $+200$ °C ( $-4$ to $+392$ °F)	screws made of A4	[[206]]0622	FN 200	5.0 (11.03)	UH



Item	Designation	Material	Measuring range	Nominal pressure	Weight	Option <sup>1)</sup>
			[bar (psi)]	-	[kg (lb)]	
A	Threaded, ISO 228 G ½ A EN837 with PTFE seal -40 to +260 °C (-40 to +500 °F)	AISI 316L,	≤ 40 (580)	PN 40	1.43 (3.15)	UC <sup>2)</sup>
В	Threaded, ANSI ½ MNPT with PTFE seal -40 to +260 °C (-40 to +500 °F)	screws made of A4	≥ 40 (000)	F1N 40	1.45 (5.15)	UD <sup>2)</sup>

1) Product Configurator, order code for "Process connection"


2) In combination with silicone oil, inert oil and plant oil.



Item	Designation	Material	Measuring range	Nominal pressure	Weight	Option <sup>1)</sup>
			[bar (psi)]		[kg (lb)]	
А	Threaded, ISO 228 G $\frac{1}{2}$ A EN837 with metal seal (silver-plated) -60 to +400 °C (-76 to +752 °F)	AISI 316L,	≤ 40 (580)	PN 40	$1.29 \log (2.04 lb)$	UC <sup>2)</sup>
В	Threaded, ANSI $\frac{1}{2}$ MNPT with metal seal (silver-plated) -60 to +400 °C (-76 to +752 °F)	screws made of A4	≤ 40 (000)	FIN 40	1.38 kg (3.04 lb)	UD <sup>2)</sup>

1) Product Configurator, order code for "Process connection"


2) In combination with high-temperature oil.



Item	Designation	Material	Measuring range	Nominal pressure 1)	Weight	Option <sup>2)</sup>
			[bar (psi)]		[kg (lb)]	
A	Threaded, ISO 228 G $\frac{1}{2}$ A EN837, with integrated seal lip -60 to +400 °C (-76 to +752 °F)	AISI 316L,	> 40 (580)	PN 400	4.75 (10.47)	UC
В	Threaded, ANSI ½ MNPT, with integrated seal lip -60 to +400 °C (-76 to +752 °F)	screws made of A4				UD


1) This separator is assembled prior to delivery and must not be disassembled!

## With TempC process membrane



Item	Designation	Material	Measuring range	PN	Weight	Option <sup>1)</sup>
			bar (psi)		kg (lb)	
А	Threaded, ISO 228 G <sup>1</sup> / <sub>2</sub> EN 837 with metal seal (silver-plated) $-60$ to $+400$ °C ( $-76$ to $+752$ °F)	AISI 316L	≤ 40 (580)	PN 40	2.35 kg (5.18 lb)	UC
В	Threaded, ASME MNPT $\frac{1}{2}$ with metal seal (silver-plated) -60 to +400 °C (-76 to +752 °F)	Screws made of A4			2.35 kg (5.18 lb)	UD

1) Product Configurator, "Process connection" ordering feature




Item	Designation	Weight in kg (lb)		Option <sup>1)</sup>
		Housing (T14 or T17)	Mounting bracket	
A	Dimensions with T14 housing, optional side display	→ 🗎 53	0.5 (1.10)	U
В	Dimensions with T17 housing, optional side display		0.5 (1.10)	0

1) Product Configurator, order code for "Additional options 2", version "G"

Also available for order as a separate accessory: part number 71102216

## Flushing rings



Use flushing rings if there is a risk of medium buildup or clogging at the process connection. The flushing ring is fitted between the process connection and the process connection provided by the customer.

Using the two lateral flushing holes, medium buildup or clogging in front of the process isolating diaphragm can be rinsed away and the pressure chamber vented.

Various nominal widths and forms allow adaption to the respective process flange.

For other details (dimension, weight, materials), see SD01553P/00/EN "Mechanical accessories for pressure measuring devices".

### Order options

Flushing rings can be ordered as a separate accessory or as an order option for the device.

Material	Nominal diameter	Approval <sup>1)</sup>	Accessory <sup>2)</sup>	Order option <sup>3) 4)</sup>		
			Part number	PMP75		
	EN1092-1	EN1092-1				
	DN25	-	71377379	PO		
	DN50	-	71377380	PP		
AISI 316L	DN80	-	71377383	PQ		
AISI J I OL	ASME B16.5					
	NPS 1"	-	71377369	РК		
	NPS 2"	CRN	71377370	PL		
	NPS 3"	CRN	71377371	РМ		

1) CSA approval: Product Configurator, order code for "Approval"

2) Inspection certification according to EN10204-3.1 material

3) Product Configurator order code for "Accessories enclosed"

4) Certificates ordered with the equipment (3.1 material certificate and NACE declaration of conformity and PMI tests) apply to the transmitters and flushing rings listed in the table.

Endress+Hauser offers additional flushing rings as Technical Special Products (TSP).


Component	Weight
Housing	See "Housing" section
Process connection	See "Process connections" section
Temperature isolator	0.34 kg (0.75 lb)
Capillary with armoring made of AISI 316L (1.4404)	0.16 kg/m (0.35 lb/m) + 0.35 kg (0.77 lb)
Capillary with armoring made of AISI 316L (PVC)	0.21 kg/m (0.46 lb/m) + 0.35 kg (0.77 lb)
Capillary with armoring made of AISI 316L (PTFE)	0.29 kg/m (0.64 lb/m) + 0.35 kg (0.77 lb)

Weight


# Materials not in contact with process

## ith Transmitter housing






Item number	Component part	Material	
1	T14 housing, RAL 5012 (blue)	<ul> <li>Die-cast aluminum with protective powder-coating on polyester base</li> <li>Thread coating: Heat-curing lubricant varnish</li> </ul>	
1	T14 housing	<ul> <li>Precision casting AISI 316L (1.4435)</li> <li>Thread coating: Heat-curing lubricant varnish</li> </ul>	
2	Cover, RAL 7035 (gray)	Die-cast aluminum with protective powder-coating or polyester base	
		Precision cast AISI 316L (1.4435) (cover made of 316L if T14 housing made of 316L)	
4	Nameplates	<ul> <li>AISI 316L (1.4404), if T14 housing is precision-cast</li> <li>Anodized aluminum, if housing T14/T15 of die-cast aluminum</li> </ul>	
5	Pressure compensation filter	AISI 316L (1.4404) and PBT-FR	
6	Pressure compensation filter, O- ring	VMQ or EPDM	
7	Sight glass	Mineral glass	
8	Sight glass seal	Silicone (VMQ)	
9	Screw	A4	
10	Sealing ring	EPDM	
11	Snap ring	PA66-GF25	
12	Snap ring for nameplates	AISI 304 (1.4301)/AISI 316 (1.4401)	
13	External ground terminal	AISI 316L (1.4404)	
14	Cover clamp	Clamp AISI 316L (1.4435), screw A4	
15	Cable entry	Polyamide (PA) or CuZn nickel-plated	
16	Seal of cable entry and plug	Silicone (VMQ)	
17	Blind plug	PBT-GF30 FR, for dust ignition-proof and Exd: AISI 316L (1.4435)	
18	External operation (keys and key cover), RAL 7035 (gray)	Polycarbonate PC-FR, screw A4	
Devices with MID parts certificate	Seal wire	DIN 1367-0 St/Zn (soft galvanized steel)	
Devices with MID parts certificate	Seals	Pb (lead)	




Item number	Component part	Material
1	T17 housing	AISI 316L (1.4404)
2	Cover	ADI 510L (1.4404)
3	Cover seal	EPDM
4	Nameplates	Lasered on
5	Pressure compensation filter	AISI 316L (1.4404) and PBT-FR
6	Pressure compensation filter, O-ring	VMQ or EPDM
7	Sight glass for non-hazardous area, ATEX Ex ia, NEPSI Zone 0/1 Ex ia, IECEx Zone 0/1 Ex ia, FM NI, FM IS, CSA IS	Polycarbonate (PC)
8	Sight glass for ATEX 1/2 D, ATEX 1/3 D, ATEX 1 GD, ATEX 1/2 GD, ATEX 3 G, FM DIP, CSA dust ignition-proof	Mineral glass
9	Sight glass seal	EPDM
10	Screw	A2-70
11	Sealing ring	EPDM
12	Snap ring	PA6
13	Screw	A4-50 Thread coating: Heat-curing lubricant varnish
14	External ground terminal	AISI 316L (1.4404)
15	Cable entry	Polyamide (PA), for dust ignition- proof: CuZn nickel-plated
16	Seal of cable entry and plug	Silicone (VMQ)
17	Blind plug	PBT-GF30 FR, for dust ignition-proof: AISI 316L (1.4435)
Devices with MID parts certificate	Seal wire	DIN 1367-0 St/Zn (soft galvanized steel)
Devices with MID parts certificate	Seals	Pb (lead)

## **Connecting parts**



Item number	Component part	Material
1	Connection between the housing and process connection	AISI 316L (1.4404)
2	Mounting bracket	Bracket AISI 316L (1.4404)
3		Screw and nuts A4-70
4		Half-shells: AISI 316L (1.4404)
5	Seal for cable from separate housing	EPDM
6	Gland for cable from separate housing	AISI 316L (1.4404)
7	PE cable for separate housing	Abrasion-proof cable with strain-relief Dynema members; shielded using aluminum-coated foil; insulated with polyethylene (PE-LD), black; copper wires, twisted, UV-resistant
8	FEP cable for separate housing	Abrasion-proof cable; shielded using galvanized steel wire netting; insulated with fluorinated ethylene propylene (FEP), black; copper cores, twisted, UV-resistant
9	Process connection adapter for separate housing	AISI 316L (1.4404)
10	Cell body	AISI 316L (1.4404)
11	Connection between body of measuring cell and capillary	AISI 316L (1.4404)
12	Heat-shrink tube (available only if capillary has PTFE or PVC sheath)	Polyolefin



Position	Component part	A Standard <sup>1)</sup> Armor for capillary	B PVC-coated Armor for capillary	C PTFE hose Armor for capillary
1	Capillary	AISI 316 Ti (1.4571)	AISI 316 Ti (1.4571)	AISI 316 Ti (1.4571)
2	Protective hose for capillary	AISI 316L (1.4404) <sup>2)</sup>	AISI 316L (1.4404)	AISI 316L (1.4404)
3	Coating/armor	-	PVC <sup>3)</sup>	PTFE <sup>4)</sup>
4	Single-ear clamp	-	-	1.4301
5	Shrink tubing at capillary junction	-	Polyolefin	-

1) If no option is specified when ordering, order option "SA" is supplied.

2) Product Configurator, order code for "Armor for capillary:" option "SA"

3) Product Configurator, order code for "Armor for capillary:" option "SB"

4) Product Configurator, order code for "Armor for capillary:" option "SC"

Materials in contact with process

## NOTICE

Device components in contact with the process are listed in the "Mechanical construction"  $\rightarrow \cong 52$  and "Ordering information"  $\rightarrow \cong 131$  sections.

#### Delta-ferrite content

A delta-ferrite content of  $\leq$  3% can be guaranteed and certified for the wetted parts if option "8" is selected in the "Additional options 1" or "Additional options 2" order code in the Product Configurator.

If the PMC71 with hygienic process connections is selected, a delta-ferrite content of  $\leq 1\%$  can be guaranteed and certified if option "8" is selected in the "Additional options 1" or "Additional options 2" order code in the Product Configurator.

#### TSE Certificate of Suitability (Transmissible Spongiform Encephalopathy)

The following applies to all device components in contact with the process:

- They do not contain any materials derived from animals.
- No additives or operating materials derived from animals are used in production or processing.

### **Process connections**

- "Clamp connections" and "Hygienic process connections": AISI 316L (DIN/EN material number 1.4435)
- Endress+Hauser supplies threaded process connections and DIN/EN flanges in stainless steel according to AISI 316L (DIN/EN material number 1.4404 or 1.4435). With regard to their stability-temperature property, the materials 1.4404 and 1.4435 are grouped together under 13EO in EN 1092-1: 2001 Tab. 18. The chemical composition of the two materials can be identical.
- Some process connections are also available in Alloy C276 (DIN/EN material number 2.4819). For this purpose see the information in the "Mechanical construction" section.

### Process membrane

Sensor	Designation	Option 1)
PMC71	$Al_2O_3$ aluminum oxide ceramic FDA, ultrapure 99.9 % <sup>2)</sup> Ceraphire <sup>®</sup> (see also www.endress.com/ceraphire)	Standard
	AISI 316L	1
PMP71	AISI 316L with gold-rhodium coating	6
	Alloy C276 (2.4819)	2
	AISI 316L with gold coating (25 $\mu m$ ), TempC $^{3)}$	G
	AISI 316L	1
	AISI 316L, TempC <sup>3)</sup>	E
	AISI 316L with gold-rhodium coating	6
PMP75	AISI 316L with 0.25 mm (0.01 in) PTFE coating	8
	Alloy C276 (2.4819)	2 4)
	Monel (2.4360)	3 4)
	AISI 316L with gold coating	4
	Tantalum (UNS R05200)	5 <sup>4)</sup>

- 1) Product Configurator, order code for "Membrane material"
- 2) The US Food & Drug Administration (FDA) has no objections to the use of ceramics made from aluminum oxide as a surface material in contact with foodstuffs. This declaration is based on the FDA certificates of our ceramic suppliers
- 3) The TempC gold-plated membrane does not offer corrosion protection!
- 4) The material of the flange raised face is the same material as is used for the process membrane. For devices with a barrel (extended diaphragm seal), the raised face of the flange and the barrel pipe are made from 316L.

#### Seals

Device	Designation	Option <sup>1)</sup>
	FKM Viton	А
	FKM Viton, FDA	G
	EPDM	В
	FFKM Perlast G75LT	С
	Kalrez	D
PMC71	Chemraz	Е
	NBR (FDA)/3A: HNBR (FDA)	F
	FKM Viton, cleaned for PWIS-free applications	L
	Kalrez, cleaned for PWIS-free applications	М
	FKM Viton, cleaned from oil and grease	1
	FKM Viton, cleaned for oxygen service, observe pressure and temperature application limits	2

1) Product Configurator, order code for "Seal"

# Fill fluid

# PMP71

Designation	Option <sup>1)</sup>
Silicone oil	А
Inert oil	F
Inert oil, cleaned from oil and grease	К
Inert oil, cleaned for oxygen service (observe application limits pressure/temperature)	Ν

1) Product Configurator, order code for "Fill fluid"

# PMP75

Designation	Option <sup>1) 2)</sup>
Silicone oil (food-safe FDA 21 CFR 175.105)	А
m capillary, inert oil	В
ft capillary, inert oil	С
Vegetable oil (food-safe FDA 21 CFR 172.856)	D
Inert oil	F
High-temperature oil, temperature isolator	G
Silicone oil, temperature isolator (food-safe FDA 21 CFR 175.105)	Н
Vegetable oil, temperature isolator	J
Inert oil, cleaned from oil and grease	К
Inert oil, cleaned for oxygen service	Ν
m capillary, silicone oil (food-safe FDA 21 CFR 175.105)	1
ft capillary, silicone oil (food-safe FDA 21 CFR 175.105)	2
m capillary, high-temperature oil	3
ft capillary, high-temperature oil	4
m capillary, vegetable oil (food-safe FDA 21 CFR 172.856)	5
ft capillary, vegetable oil (food-safe FDA 21 CFR 172.856)	6
m capillary, low-temperature oil	7
ft capillary, low-temperature oil	8

1) 2)

Product Configurator, order code for "Fill fluid" For diaphragm seal devices with 3-A and EHEDG certificates, only select fill fluids with FDA approval!

# Operability

Operating concept	Operator-oriented menu structure for user-specific tasks
	<ul><li>Commissioning</li><li>Operation</li><li>Diagnosis</li></ul>
	Quick and safe commissioning
	Guided menus for applications
	Reliable operation
	<ul> <li>Local operation possible in several languages</li> <li>Standardized operation at the device and in the operating tools</li> <li>Parameters relating to measured values can be locked/unlocked using the device's write protection switch, using the device software or via remote operation</li> </ul>
	Efficient diagnostics increase measurement availability
	Pomodial massures are integrated in plain text

- Remedial measures are integrated in plain text
- Diverse simulation options

## Local operation

Function	External operation (operating keys, optional, not T17 housing)	Internal operation (electronic insert)	Onsite display (optional)
Position adjustment (zero point correction)	V	V	V
Setting lower range value and upper range value - reference pressure present at the device	✓ (HART only)	✔ (HART only)	V
Device reset	V	V	~
Locking and unlocking parameters relevant to the measured value	_	V	~
Value acceptance indicated by the green LED	V	V	V
Switching damping on and off	✓ (only if display is connected)	✓ (HART and PA only)	V
Configuring the bus address of the device (PA)		V	V
Switching simulation mode on and off (FOUNDATION Fieldbus)		~	V

## Operating the device using onsite display (optional)

A 4-line liquid crystal display (LCD) is used for display and operation. The onsite display shows measured values, dialog text as well as fault and notice messages in plain text, thereby supporting the user in every stage of operation.

The display can be removed for easy operation.


The device display can be turned in 90° steps.

Depending on the installation position of the device, this makes it easy to operate the device and read the measured value.

# Functions:

- 8-digit measured value display including sign and decimal point and bar graph for
  - 4 to 20 mA HART (bar graph from 4 to 20 mA)
  - 1-5V DC (bar graph from 1 to 5 volt)
  - PROFIBUS PA (bar graph as graphic display of standardized value of AI block)
  - FOUNDATION Fieldbus (bar graph as graphic display of transducer output).
- -
- Simple and complete menu guidance due to breakdown of parameters into several levels and groups.
- Menu guidance in up to 8 languages
- Each parameter is given a 3-digit ID number for easy navigation.
- Option for configuring the display according to individual requirements and preferences, such as language, alternating display, display of other measured values such as sensor temperature, contrast setting.
- Comprehensive diagnostic functions (fault and warning message, peak-hold indicators, etc.).
- Rapid and safe commissioning with the Quick Setup menus


#### Overview



- 1 Operating keys
- 2 Bargraph
- 3 Symbol
- 4 Header
- 5 Parameter ID number

### Operating keys on the exterior of the device

With the aluminum housing (T14), the operating keys are located either outside on the housing, under the protection cap or inside on the electronic insert. With the stainless steel housing (T17), the operating keys are always located inside the housing on the electronic insert.



- A 1-5V DC and 4 to 20 mA HART
- B PROFIBUS PA and FOUNDATION Fieldbus

The operating keys located externally on the device work on the Hall sensor principle. As a result, no additional openings are required in the device. This guarantees:

- Complete protection against environmental influences such as moisture and contamination.
- Simple operation without any tools.
- No wear.

Ordering information:


Product Configurator, order code for "Output, operation"

# Operating keys and elements located internally on the electronic insert

Ordering information:


Product Configurator, order code for "Output, operation"

# HART




- 1 DIP switch for locking/unlocking parameters relevant to the measured value
- 2 DIP switch for switching damping on/off
- 3 Green LED to indicate value being accepted
- 4 Operating keys
- 5 Slot for optional display
- 6 Slot for optional HistoROM<sup>®</sup>/M-DAT

# 1-5V DC




- 1 DIP switch for locking/unlocking parameters relevant to the measured value
- 2 DIP switch for switching damping on/off
- 3 DIP switch for alarm voltage/alarm current SW / alarm min (0.9 V/~3.6 mA)
- 4...5 Not assigned
- 6 Green LED to indicate value being accepted
- 7 Slot for display

# PROFIBUS PA



- 1 DIP switch for locking/unlocking parameters relevant to the measured value
- 2 DIP switch for switching damping on/off
- *3 Green LED to indicate value being accepted*
- 4 Key for position adjustment and device reset
- 5 DIP switch for bus address
- 6 Slot for optional display
- 7 Slot for optional HistoROM®/M-DAT

### FOUNDATION Fieldbus



- 1 DIP switch for locking/unlocking parameters relevant to the measured value
- 2 DIP switch for simulation mode on/off
- *3 Green LED to indicate value being accepted*
- 4 Key for position adjustment and device reset
- 5 Slot for optional display
- 6 Slot for optional HistoROM®/M-DAT

Remote operation

All software parameters are accessible depending on the position of the write protection switch on the device.

Hardware and software for remote operation		PROFIBUS PA	FOUNDATION Fieldbus
FieldCare	r	V	V
FieldXpert SFX100	~	_	V

Hardware and software for remote operation 1)	HART	PROFIBUS PA	FOUNDATION Fieldbus
NI-FBUS Configurator		_	V
HistoROM <sup>®</sup> /M-DAT	v	<b>v</b>	V

1) Not for 1-5V DC

#### FieldCare

FieldCare is an Endress+Hauser asset management tool based on FDT technology. With FieldCare, you can configure all Endress+Hauser devices as well as devices from other manufacturers that support the FDT standard.

FieldCare supports the following functions:

- Configuration of transmitters in offline and online mode
- Device data upload/download (not for 1-5V DC)
- HistoROM<sup>®</sup>/M-DAT analysis
- Documentation of the measuring point

Connection options:

- HART via Commubox FXA195 and USB interface of a computer
- PROFIBUS PA via segment coupler and PROFIBUS interface card
- Service interface with Commubox FXA291 and ToF adapter FXA291 (USB).

For further information, please contact your local Endress+Hauser Sales Center.

#### Field Xpert SFX100

Field Xpert is an industrial PDA with integrated 3.5" touchscreen from Endress+Hauser based on Windows Mobile. It offers wireless communication via the optional VIATOR Bluetooth modem from Endress+Hauser. Field Xpert also works as a stand-alone device for asset management applications. For details, refer to BA00060S/04/EN.

#### **Commubox FXA195**

For intrinsically safe HART communication with FieldCare via the USB interface. For details refer to TI00404F/00/EN.

### Commubox FXA291

The Commubox FXA291 connects Endress+Hauser field devices with a CDI interface (=Endress +Hauser Common Data Interface) to the USB interface of a personal computer or a notebook. For details refer to TI00405C/07/EN.



For the following Endress+Hauser devices you need the "ToF adapter FXA291" as an additional accessory:

- Cerabar S PMC71, PMP7x
- Deltabar S PMD7x, FMD7x
- Deltapilot S FMB70

#### **ToF Adapter FXA291**

The ToF adapter FXA291 connects the Commubox FXA291 with devices of the ToF platform, pressure equipment and Gammapilot via the USB interface of a personal computer or a notebook. For details refer to KA00271F.

#### Profiboard

For connecting a PC to the PROFIBUS.

#### Proficard

For connecting a laptop to the PROFIBUS.

## FF configuration program

- FF configuration program, such as NI-FBUS Configurator, to
- connect devices with "FOUNDATION Fieldbus signal" into an FF-network
- set FF-specific parameters

	Operation with NI-FBUS Configurator:						
	The NI-FBUS Configurator is an easy-to-use graphical environment for creatin a schedule based on the fieldbus concepts.	g linkages, loops, and					
	<ul> <li>You can use the NI-FBUS Configurator to configure a fieldbus network as follow</li> <li>Set block and device tags</li> <li>Set device addresses</li> <li>Create and edit function block control strategies (function block applications</li> <li>Configure vendor-defined function and transducer blocks</li> <li>Create and edit schedules</li> <li>Read and write to function block control strategies (function block application</li> <li>Invoke methods specified in the manufacturer-specific DD (e.g. basic device)</li> <li>Display DD menus (e.g. tab for calibration data)</li> <li>Download a configuration</li> <li>Verify a configuration and compare it to a saved configuration</li> <li>Replace devices</li> <li>Save and print a configuration</li> </ul>	s) ons)					
HistoROM®/M-DAT (optional)	The HistoROM <sup>®</sup> /M-DAT is a memory module that can be attached to any electronic insert (not for 1-5V DC). HistoROM <sup>®</sup> /M-DAT can be retrofitted at any stage (order number: 52027785).						
	<ul> <li>Your benefits</li> <li>Quick and safe commissioning of the same measuring points by copying the one transmitter to another transmitter.</li> <li>Reliable process monitoring thanks to cyclical recording of pressure and sense measured values</li> <li>Simple diagnosis by recording diverse events such as alarms, configuration of measuring range undershoot and overshoot for pressure and temperature as overshoot and undershoot for pressure and temperature etc.</li> <li>Analysis and graphic evaluation of the events and process parameters via so scope of supply).</li> </ul>	sor temperature hanges, counters for s well as user limit					
	You can copy data from one transmitter to another transmitter when operatin Fieldbus device via an FF configuration program. You need the Endress+Hause program, the Commubox FXA291 service interface and the ToF adapter FXA2 the data and events saved in the HistoROM <sup>®</sup> /M-DAT.	er FieldCare operating					
	Ordering information:						
	Product Configurator, order code for "Additional options:", version "N" or						
	Product Configurator, order code for "Application package:", option "EN" or						
	as a separate accessory (part no.: 52027785).						
	For further information, please contact your local Endress+Hauser Sales Center.						
System integration	The device can be given a tag name (max. 8 alphanumeric characters).						
	Designation	Option <sup>1)</sup>					
	Measuring point (TAG), see additional specifications	Z1					

1) Product Configurator, order code for "Identification"

Bus address, see additional spec.

Z2

# Planning instructions for diaphragm seal systems

# NOTICE

# Diaphragm seal systems sized/ordered incorrectly

The performance and the permitted range of application of a diaphragm seal system depend on the process membrane used, the fill fluid, the coupling, the design and on the process and ambient conditions present in the individual application.

To help you select the right diaphragm seal systems for your particular applications, Endress
 +Hauser provides its customers with the "Applicator Sizing Diaphragm Seal" selection tool, which is available free of charge at "www.endress.com/applicator" or as a download.

Home	e > Pressure > Product Sizing > Diaphragm Seal							Help Contact
	Sizing Diaphragm Seal					Dimensionin	ig pressure devices	
	Sizing Chart Extended Order Code							
	General parameters							
	Product 1 Cerabar S PMP75		$\sim$				1	
	TAG			Extended Order Code	PMP75-	1H11B3A	1	
							ette	
	1 Message(s)							
	Transmitter data			Measurement accuracy and o	ffrat 1		~	
		uni	t			% span /10K 🗸 🗸	mbar/10K 🗸	
	Sensor 1 1bar/100kPa/15psi gauge	$\sim$		Error due to change in process		0.048	0.477	
	Adjusted span 1 000	ml	bar 🗸 🗸	temperature		0.046	0.477	
	Print Sizing Add to Cart						Reset	

i

For further details, or for information on an optimum diaphragm seal solution, your local Endress+Hauser Sales Center is also always happy to help.

Applications

Diaphragm seal systems should be used if the process and the device need to be separated. Diaphragm seal systems offer clear advantages in the following instances:

- In the case of extreme process temperatures
- For aggressive media
- In the case of process media that crystallize
- In the case of corrosive or highly various process media or process media with solids content
- In the case of heterogeneous and fibrous process media
- If extreme measuring point cleaning is necessary, or in the event of very damp mounting locations
- If the measuring point is exposed to severe vibrations
- For mounting locations that are difficult to access

# Design and mode of operation

Diaphragm seals act as separators between the measuring system and the process.

- A diaphragm seal system consists of:
- A diaphragm seal
- A capillary tube or temperature isolator where applicable
- Fill fluid
- A pressure transmitter.

The process pressure acts via the process membrane of a diaphragm seal on the liquid-filled system, which transfers the process pressure to the sensor of the pressure transmitter.

Endress+Hauser delivers all diaphragm seal systems as welded versions. The system is hermetically sealed, which ensures greater reliability.

The diaphragm seal determines the application range of the system on the basis of

- The diameter of the process membrane
- The stiffness and material of the process membrane
- The design (oil volume)

#### Diameter of the process membrane

The greater the diameter of the process membrane (less stiff), the smaller the temperature effect on the measurement result.

#### Stiffness of the process membrane

The stiffness depends on the diameter of the process membrane, the material, any existing coating, and the thickness and shape of the process membrane. The thickness of the process membrane and the shape are determined by the design. The stiffness of a process membrane of a diaphragm seal influences the temperature application range and the measured error caused by temperature effects.

# The Endress+Hauser TempC Membrane: Highest accuracy and process safety when measuring pressure and differential pressure using diaphragm seals

To measure with even greater accuracy in these applications and to increase process safety, Endress +Hauser has developed the TempC Membrane which is based on a completely revolutionary technology. This membrane guarantees the utmost level of accuracy and process safety in diaphragm seal applications.

- The very low temperature effect minimizes the effect of process and ambient temperature fluctuations, thereby guaranteeing accurate and reliable measurements. Measurement inaccuracies caused by temperature are reduced to a minimum.
- The TempC Membrane can be used at temperatures between -70 °C (-94 °F) and +400 °C (+752 °F). This guarantees maximum process safety even for very long sterilization and cleaning cycles (SIP/CIP) in tanks and pipes at high temperatures.
- Smaller instrumentation dimensions are possible thanks to the TempC Membrane. With a smaller process connection, the new membrane measures at least as accurately as a conventional membrane with a larger diameter.
- Due to the geometry of the membrane, an overshoot occurs initially immediately following a temperature shock. This results in a transient response, the duration and deviation of which are significantly less compared to traditional membrane types. In the case of batch processes, these shorter recovery times mean a far higher level of availability of the production facilities. In the case of TempC Membranes, the effect of the overshoot on the output signal can be reduced by adjusting the damping.

Ordering information:

See the Product Configurator for the individual process connection and the choice of process membrane.

Selection in the Applicator:

Under "Transmitter data" in the "Membrane material" field.

### Capillary

As standard, capillaries with an internal diameter of 1 mm (0.04 in) are used.

The capillary tube influences the thermal change, the ambient temperature operating range and the response time of a diaphragm seal system as a result of its length and internal diameter.

#### Fill fluid

The medium and ambient temperatures as well as the process pressure are very important factors to be considered when selecting the fill fluid. Pay attention to the temperatures and pressures during commissioning and cleaning. Another selection criterion is the compatibility of the fill fluid with the requirements of the medium. For example, only fill fluids that do not present a health hazard may be used in the food industry, e.g. vegetable oil or silicone oil (see also the following section "Diaphragm seal fill fluids").

The fill fluid used influences the thermal change, the temperature application range of a diaphragm seal system and the response time. A temperature change causes a volume change in the fill fluid. The volume change is dependent on the expansion coefficient and on the volume of the fill fluid at calibration temperature (constant in range: +21 to +33 °C (+70 to +91 °F)). The application range can be extended by a fill fluid with a lower expansion coefficient and a shorter capillary.

For example, the fill fluid expands in the event of a temperature increase. The additional volume presses against the process membrane of a diaphragm seal. The stiffer a process membrane is, the greater its return force, which counteracts a volume change and acts together with the process pressure on the measuring cell, thus shifting the zero point.

#### Pressure transmitter

The pressure transmitter influences the temperature operating range, the TC zero point and the response time as a result of its volume change. The volume change is the volume that has to be shifted to pass through the complete measuring range.

Pressure transmitters from Endress+Hauser are optimized with regard to minimum volume change.

# Diaphragm seal filling oils

Medium	$P_{abs} = 0.05 \text{ bar } (0.725 \text{ psi})^{1)}$	$P_{abs} = \ge 1 \text{ bar (14.5 psi)}^{2)}$
Silicone oil	-40 to +180 °C (-40 to +356 °F)	-40 to +250 °C (-40 to +482 °F)
High-temperature oil	-20 to +200 °C (-4 to +392 °F)	-20 to +400 °C (-4 to +752 °F) <sup>3) 4) 5)</sup>
Low-temperature oil	-70 to +120 °C (-94 to +248 °F)	-70 to +180 °C (-94 to +356 °F)
Vegetable oil	-10 to +160 °C (+14 to +320 °F)	-10 to +220 °C (+14 to +428 °F)
Inert oil	-40 to +100 °C (-40 to +212 °F)	-40 to +175 °C (-40 to +347 °F) <sup>6) 7)</sup>

1) Permitted temperature range at  $p_{abs} = 0.05$  bar (0.725 psi) (observe temperature limits of the device and the system!)

2) Permitted temperature range at  $p_{abs} \ge 1$  bar (14.5 psi) (observe temperature limits of the device and the system!)

3) 325 °C (617 °F) at  $\geq$ 1 bar (14.5 psi)absolute pressure.


4) 350 °C (662 °F) at ≥1 bar (14.5 psi) absolute pressure (max. 200 hours).

5) 400 °C (752 °F) at  $\geq$ 1 bar (14.5 psi) absolute pressure (max. 10 hours).

6) 150 °C (302 °F) at  $\geq$ 1 bar (14.5 psi)absolute pressure.

7) 175 °C (347 °F) at  $\geq$ 1 bar (14.5 psi) absolute pressure (max. 200 hours).

The calculation of the operating temperature range of a diaphragm seal system depends on the fill fluid, capillary length and capillary internal diameter, process temperature and oil volume of the diaphragm seal. Detailed calculations, e.g. for temperature ranges, vacuum pressure ranges and temperature ranges, are done separately in the Applicator "Sizing Diaphragm Seal".



# Capillary


In order to obtain more precise measurement results and to avoid a defect in the device, mount the capillaries as follows:

- Vibration-free (in order to avoid additional pressure fluctuations)
- Not in the vicinity of heating or cooling lines
- Insulate the capillaries if the ambient temperature is below or above the reference temperature
- With a bending radius ≥ 100 mm (3.94 in)
- When using diaphragm seal systems with a capillary, sufficient strain relief must be provided to
  prevent the capillary from bending (capillary bending radius ≥ 100 mm (3.94 in)).
- In the case of devices with diaphragm seals and capillaries, the zero point shift caused by the hydrostatic pressure of the filling liquid column in the capillaries must be taken into account when selecting the measuring cell. If a measuring cell with a small measuring range is selected, a position adjustment can cause range violation.

#### Thermal insulation

#### Thermal insulation with diaphragm seal directly mounted


The PMP75 must only be insulated up to a certain height. The maximum permitted insulation height is indicated on the devices and applies to an insulation material with a heat conductivity  $\leq 0.04$  W/(m x K) and to the maximum permitted ambient and process temperature. The data were determined under the most critical application "quiescent air". Maximum permitted insulation height, here indicated on a PMP75 with a flange:



A Ambient temperature

- B Process temperature
- 1 Maximum permitted insulation height
- 2 Insulation material

# Installation with direct mounting



 $T_a$  Ambient temperature at transmitter

 $T_p$  Maximum process temperature


T <sub>a</sub>	T <sub>p</sub>
+85 °C (+185 °F)	-70 to +120 °C (-94 to +248 °F)
+60 °C (+140 °F)	-70 to +160 °C (-94 to +320 °F)
−20 °C (−4 °F)	-70 to +160 °C (-94 to +320 °F)
−50 °C (−58 °F)	0 to +160 °C (+32 to +320 °F)

### Mounting with temperature isolator

Use of temperature isolators in the event of constant extreme medium temperatures which cause the maximum permissible electronics temperature of +85 °C (+185 °F) to be exceeded. Diaphragm seal systems with temperature isolators can be used up to a maximum temperature of +400 °C (+752 °F) depending on the fill fluid used. . To minimize the influence of rising heat, mount the device horizontally or with the housing pointing downwards. The additional installation height causes a zero point shift of maximum 21 mbar (0.315 psi) due to the hydrostatic column in the temperature isolator. This zero point shift can be corrected on the device.

The maximum ambient temperature  $T_{\rm a}$  at the transmitter depends on the maximum process temperature  $T_{\rm p}.$ 

The maximum process temperature depends on the diaphragm seal fill fluid used.



A No insulation

B Insulation 30 mm (1.18 in)

- C Maximum insulation
- 1 Transmitter
- 2 Insulation material

Item	T <sub>a</sub> <sup>1)</sup>	T <sub>p</sub> <sup>2)</sup>
A	60 °C (140 °F)	400 °C (752 °F) <sup>3)</sup>
	85 °C (185 °F)	200 °C (392 °F)
	−50 °C (−58 °F)	60 °C (140 °F)
	−35 °C (−31 °F)	−70 °C (−94 °F)
В	80 °C (176 °F)	400 °C (752 °F) <sup>3)</sup>
	85 ℃ (185 ℉)	300 ℃ (572 ℉)

Item	T <sub>a</sub> <sup>1)</sup>	T <sub>p</sub> <sup>2)</sup>
	−50 °C (−58 °F)	130 °C (266 °F)
	−35 °C (−31 °F)	−70 °C (−94 °F)
С	67 °C (153 °F)	400 °C (752 °F) <sup>3)</sup>
	85 °C (185 °F)	200 °C (392 °F)
	−50 °C (−58 °F)	70 ℃ (158 ℉)
	−35 °C (−31 °F)	−70 °C (−94 °F)

1) 2) 3)

Maximum ambient temperature at transmitter Maximum process temperature Process temperature: max. +400 °C (+752 °F), depending on the diaphragm seal fill fluid used


# Vacuum applications

### Mounting instructions


For vacuum applications, pressure transmitters with a ceramic measuring membrane (oil-free) are preferable.

For applications under vacuum, Endress+Hauser recommends mounting the pressure transmitter below the diaphragm seal. This prevents vacuum loading of the diaphragm seal caused by the presence of fill fluid in the capillary.

When the pressure transmitter is mounted above the diaphragm seal, the maximum height difference H1 in accordance with the diagrams below must not be exceeded. The following graphic describes installation above the lower diaphragm seal:



The maximum height difference depends on the density of the fill fluid and the smallest ever pressure that is permitted to occur at the diaphragm seal (empty vessel), see the diagram below. The following diagram depicts the maximum installation height above the diaphragm seal for vacuum applications.



- Α Height difference H1
- В Pressure at diaphragm seal
- Low-temperature oil 1
- 2 Vegetable oil
- 3 Silicone oil
- 4 High-temperature oil
- 5 Inert oil

CE mark	The device meets the legal requirements of the relevant EC directives. Endress+Hauser confirms that the device has been successfully tested by applying the CE mark.
RoHS	The measuring system complies with European Directive 2002/96/EC.
RCM-Tick marking	The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products bear the RCM-Tick marking on the nameplate.
	A002956-
Ex approvals	<ul> <li>ATEX</li> </ul>
	<ul> <li>FM</li> <li>CSA</li> <li>NEPSI</li> <li>IECEx</li> <li>TIIS</li> </ul>
	• Also combinations of different approvals All explosion protection data are given in separate documentation which is available upon request. The Ex documentation is supplied as standard with all Ex-systems $\rightarrow \cong 135$ .
EAC conformity	The measuring system meets the legal requirements of the applicable EAC guidelines. These are listed in the corresponding EAC Declaration of Conformity along with the standards applied.
	Endress+Hauser confirms successful testing of the device by affixing to it the EAC mark.
Suitable for hygiene	For information on installation and approvals, see documentation SD02503F "Hygiene approvals".
applications	For information on 3-A and EHEDG-tested adapters, see documentation TI00426F "Weld-in adapter, process adapter and flanges".
Certificate of current Good	Product Configurator, order code for "Test, Certificate" option "JG"
Manufacturing Practices (cGMP)	<ul> <li>The certificate is only available in English</li> <li>Materials of construction of product wetted parts</li> <li>TSE compliance</li> <li>Polishing and surface finish</li> </ul>
	<ul> <li>Material/ compound compliance table (USP Class VI, FDA conformity)</li> </ul>
Functional safety SIL/ IEC 61508 Declaration of Conformity (optional)	The Cerabar S with 4 to 20 mA output signal has been developed in accordance with the IEC 61508 standard. These devices can be used to monitor the process level and pressure up to SIL 3. For a detailed description of safety functions with the Cerabar S, settings and functional safety data, see the "Functional safety manual - Cerabar S" SD00190P/00.
	For devices up to SIL 3 / IEC 61508 Declarations of Conformity see:
	Ordering information: Product Configurator, order code for "Additional options 1" and "Additional options 2", version "E".
Overfill prevention	WHG (see document ZE00260P/00/EN)
	Ordering information:
	Product Configurator, order code for "Approval", option "6".

# Certificates and approvals

CRN approval	A CRN approval is available for some device versions. A CRN-approved process connection with a CSA approval must be ordered for a CRN-approved device. These devices are fitted with a separate plate bearing the registration number CRN 0F10525.5C.			
	PMP75 devices with a capillary are not CRN-approved.			
	Ordering information:			
	Product Configurator, order code for "Process connection; material" and			
	Product Configurator, order code for "Approval" (only in conjunction with an approved process connection)			
Other standards and guidelines	The applicable European guidelines and standards can be found in the relevant EU Declarations of Conformity. The following standards were also applied:			
	IEC 62828-1 / DIN EN 60770 and IEC 62828-2 / DIN EN 60770:			
	Transmitters for use in industrial-process control systems. Part 1: Methods for inspection and routine testing			
	DIN 16086:			
	Electrical pressure measuring instruments, pressure sensors, pressure transmitters, pressure measuring instruments, concepts, specifications on data sheets			
	EN 61326-X:			
	EMC product family standard for electrical equipment for measurement, control and laboratory use.			
	EN 60529:			
	Degrees of protection provided by enclosures (IP code)			
	WELMEC guide 8.8:			
	General and Administrative Aspects of the Voluntary System of Modular Evaluation of Measuring instruments under the MID.			
	OIML R117-1 Edition 2007 (E):			
	Dynamic measuring systems for liquids other than water.			
	EN 12405-1/A1 Edition 2006:			
	Gas meters – Conversion devices – Part 1: Volume conversion			
Drossuro Equipmont	Pressure equipment with permitted pressure ≤ 200 bar (2 900 psi)			
Pressure Equipment Directive 2014/68/EU (PED)	Pressure equipment with permitted pressure $\leq 200$ bar (2 900 psi) Pressure equipment (maximum allowable pressure PS $\leq 200$ bar (2 900 psi)) can be classified as pressure accessories in accordance with Pressure Equipment Directive 2014/68/EU. If the maximum allowable pressure is $\leq 200$ bar (2 900 psi) and the pressurized volume of the pressure equipment is $\leq 0.1$ l, the pressure equipment is subject to the Pressure Equipment Directive (see Pressure Equipment Directive 2014/68/EU, Article 4, point 3). The Pressure Equipment Directive only requires that the pressure equipment shall be designed and manufactured in accordance with the "sound engineering practice of a Member State".			
	Reasons:			
	<ul> <li>Pressure Equipment Directive (PED) 2014/68/EU Article 4, point 3</li> <li>Pressure equipment directive 2014/68/EU, Commission's Working Group "Pressure", Guideline A-05 + A-06</li> </ul>			
	Note:			
	A partial examination shall be performed for pressure instruments that are part of safety equipmen for the protection of a pipe or vessel from exceeding allowable limits (safety accessory in accordance with Pressure Equipment Directive 2014/68/EU Article 2, point 4).			

## Pressure equipment with allowable pressure > 200 bar (2900 psi)

Pressure equipment designated for application in every process fluid having a pressurized volume of <0.1 l and a max. allowable pressure PS > 200 bar (2 900 psi) must satisfy the essential safety requirements set out in Annex I of the Pressure Equipment Directive 2014/68/EU. According to Article 13 pressure equipment shall be classified by category in accordance with Annex II. Taking into account the low volume specified above, the pressure instruments can be categorized as category I pressure equipment. They must then bear a CE mark.

#### Reasons:

- Pressure Equipment Directive 2014/68/EU, Article 13, Annex II
- Pressure equipment directive 2014/68/EU, Commission's Working Group "Pressure", Guideline A-05

#### Note:

A partial examination shall be performed for pressure instruments that are part of safety equipment for the protection of a pipe or vessel from exceeding allowable limits (safety accessory in accordance with Pressure Equipment Directive 2014/68/EU, Article 2, point 4).

#### The following also applies:

	<ul> <li>PMP71 with thread and internal process membrane PN &gt; 200 and oval flange adapter PN &gt; 200: Suitable for stable gases in group 1, category I, module A</li> <li>PMP75 with pipe diaphragm seal ≥ 1.5"/PN40: Suitable for stable gases in group 1, category II, module A2</li> <li>PMP75 with separators PN &gt; 200 ≥ 1.5"/PN40: Suitable for stable gases in group 1, category I, module A</li> <li>PMP75 with thread PN &gt; 200 ≥ 1.5"/PN40: Suitable for stable gases in group 1, category I, module A</li> <li>PMP75 with thread PN &gt; 200: Suitable for stable gases in group 1, category I, module A</li> </ul>
Manufacturer declarations	Depending on the desired configuration, the following documents can be ordered additionally with the device: • FDA conformity • TSE-free: materials free from animal origin • Regulation (EC) No. 2023/2006 (GMP) • Regulation (EC) No. 1935/2004 on materials and articles intended to come into contact with food
	Downloading the Declaration of Conformity
	www.endress.com $\rightarrow$ Download
Marine approval	<ul><li>GL (German Lloyd)</li><li>ABS</li></ul>
	Ordering information:
	Product Configurator, order code for "Additional options 1" or "Additional options 2", version "S".
Drinking water approval	PMC71/PMP71: NSF 61 approval
	PMC71/PMP71: UBA/W270 approval (ordering information as for NSF approval: Product Configurator, order code for "Additional options 1" or "Additional options 2" option "F".)
	Ordering information:
	Product Configurator, order code for "Additional options 1" or Additional options 2", version "F".
Approvals for custody transfer	All aspects of OIML R117-1 Edition 2007 (E) and EN 12405-1/A1 Edition 2006 are fulfilled.
MID Parts Certificate	TC7975

Classification of process sealing between electrical systems and (flammable or combustible) process fluids in accordance with ANSI/ISA 12.27.01 Endress+Hauser devices are designed in accordance with ANSI/ISA 12.27.01, allowing the user to waive the use of - and save the cost of installing - external secondary process seals in the conduit as required by the process sealing sections of ANSI/NFPA 70 (NEC) and CSA 22.1 (CEC). These instruments comply with the North-American installation practice and provide a very safe and cost-saving installation for pressurized applications with hazardous fluids. Please refer to the following table for the seal class assigned (single seal or dual seal):

Device	Approval	Remark	Single seal MWP	Dual seal MWP	
		W/o separate housing	-	60 bar (900 psi)	
PMC71	CSA C/US IS	With separate housing	40 bar (600 psi)	-	
	CSA C/US XP, XP+IS	W/o separate housing	400 bar (6000 psi)	-	
PMP71		W/o separate housing	>200 to 400 bar (3 000 to 6 000 psi)	≤200 bar (3000 psi)	
		With separate housing	400 bar (6000 psi)	-	
	XP, XP+IS	W/o separate housing	400 bar (6000 psi)	-	
PMP75	CSA C/US IS	W/o separate housing	>200 to 400 bar (3 000 to 6 000 psi)	≤200 bar (3000 psi)	
	CSA C/US IS	With separate housing	400 bar (6000 psi)	-	

Further information can be found in the control drawings of the relevant devices.

# Inspection certificate

Designation	PMC71	PMP71	PMP75	Option
3.1 Material documentation, wetted metal parts, EN10204-3.1 inspection certificate	V	V	V	B <sup>1) 3)</sup>
Conformity to NACE MR0175, wetted metallic parts	_	V	V	C <sup>1)3)</sup>
EN10204-3.1 material, NACE MR0175, wetted metal parts, inspection certificate	_	V	V	D <sup>1) 3)</sup>
Individual test, test report	V	V	v	3 <sup>1)</sup>
Pressure test, internal procedure, test report	V	V	V	4 <sup>1)</sup>
Helium leak test, internal procedure, test report	V	V	_	5 <sup>1)</sup>
EN10204-3.1 material wetted parts +Ra, Ra= surface roughness, dimensional check, inspection certificate	V	_	_	6 <sup>1)</sup>
Delta-Ferrite measurement, internal procedure, wetted metallic parts, inspection certificate	V	_	_	8 <sup>1)</sup>
3.1 Material documentation, wetted metal parts, EN10204-3.1 inspection certificate	V	V	V	JA <sup>2) 3)</sup>
Conformity to NACE MR0175, wetted metallic parts	V	V	V	JB <sup>2)3)</sup>
Conformity to NACE MR0103, wetted metallic parts	V	V	V	JE <sup>2)3)</sup>
Surface finish measurement ISO4287/Ra, wetted metal parts, inspection certificate	V	_	V	KB <sup>2)</sup>
Helium leak test, internal procedure, inspection certificate	V	V	V	KD 2)
Pressure test, internal procedure, inspection certificate	V	V	V	KE <sup>2)</sup>
Delta-Ferrite measurement, internal procedure, wetted metallic parts, inspection certificate	V	_	V	KF 2)
PMI test (XRF), internal procedure, metal parts in contact with the medium	V	V	v	KG <sup>2)</sup>
Welding documentation, wetted/pressurized seams	—	V	_	KS <sup>2)</sup>

1) Product Configurator, order code for "Additional options 1" and "Additional options 2"

2) Product Configurator, order code for "Test, Certificate"

3) The choice of this feature for coated process isolating diaphragms/process connections refers to the metal base material.

# Calibration

Designation	PMC71	PMP71	PMP75	Option <sup>1)</sup>
Sensor range; mbar/bar	V	r	~	1
Sensor range; kPa/MPa	v	V	V	2
Sensor range; mmH2O/mH2O	v	V	V	3
Sensor range; inH2O/ftH2O	v	r	~	4
Sensor range; psi	v	r	~	6
Factory calibration certificate, 5-point; see additional specification	V	r	~	С
DKD/DAkkS certificate; see additional specification	V	r	~	D
Customized pressure; see additional specification	v	r	V	E
Customized level; see additional specification	v	r	V	F
Customized pressure + 5-point factory calibration certificate; see additional specification	V	r	~	Н
Customized level + 5-point factory calibration certificate; see additional specification	V	r	~	Ι
Platinum; see additional specification	v	r	_	К
Platinum + factory calibration certificate 5-point; see additional specification	v	V	_	L
Platinum + DKD/DAkkS certificate; see additional specification	V	V		М

1) Product Configurator, order code for "Calibration; unit"

# Service

Designation	Option $^{1)}$ (not for 1-5V DC)
Cleaned of oil+grease <sup>2)</sup>	HA
Cleaned for oxygen service <sup>2)</sup>	HB
Cleaned of PWIS (paint-wetting impairment substances) <sup>2)</sup>	НС

1) Product Configurator, order code for "Service"

2) Device only, not accessories or enclosed accessories.

# **Ordering information**

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
   -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
   Open product page -> The "Configure" button to the right of the product image opens the Product
   Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com
  - Product Configurator the tool for individual product configuration
- Up-to-the-minute configuration data
  - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
  - Automatic verification of exclusion criteria
  - Automatic creation of the order code and its breakdown in PDF or Excel output format
  - Ability to order directly in the Endress+Hauser Online Shop

 Special device versions
 Endress+Hauser offers special device versions as Technical Special Products (TSP).

 For further information please contact your local Endress+Hauser Sales Center.

Scope of delivery 

Measuring device

Ontional accounts

- Optional accessories Brief Operating Instructions
- Brief Operating Instructions
   Calibration certificates
- Calibration certificate
   Optional certificates
- Optional certificates

Measuring point (TAG)	Order code	895: Marking
	Option	Z1: Tagging (TAG), see additional spec.
	Position of the measuring point marking	To be selected in the additional specifications: Tag plate Stainless Steel Self-adhesive paper label Supplied label/plate RFID TAG RFID TAG + Tag plate Stainless Steel RFID TAG + Self-adhesive paper label RFID TAG + Supplied label/plate
	Definition of the measuring point designation	To be defined in the additional specifications: 3 lines containing up to 18 characters each The measuring point designation appears on the selected label and/or the RFID TAG.
	Identification on electronic nameplate (ENP)	32 characters

# Configuration data sheet

# Pressure

The following configuration data sheet must be completed and included with the order if the option "E" or "H" has been selected in the Product Configurator, order code for "Calibration; Unit".

Pressure unit				
<ul><li>mbar</li><li>bar</li><li>psi</li></ul>	$\begin{array}{c c} & mmH_2O & {}^{1)} \\ \hline & mH_2O & {}^{1)} \\ \hline & ftH_2O & {}^{1)} \\ \hline & inH_2O & {}^{1)} \end{array}$	$\begin{array}{c c} mmHg ^{2)} \\ \hline nHg ^{2)} \\ gf/cm^2 \\ \hline kgf/cm^2 \end{array}$	<ul> <li>Pascal</li> <li>hPa</li> <li>kPa</li> <li>MPa</li> </ul>	<ul> <li>torr</li> <li>g/cm<sup>2</sup></li> <li>kg/cm<sup>2</sup></li> <li>lb/ft<sup>2</sup></li> <li>atm</li> </ul>

1) The conversion factor for the pressure unit is based on a reference temperature of 4 °C (39.2 °F).

2) The conversion factor of the pressure unit refers to a reference temperature of 0  $^{\circ}$ C (32  $^{\circ}$ F).

Calibration Range / Output		
Low range value (LRV): Upper range value (URV):	 [Pressure engineering unit] [Pressure engineering unit]	


Display
Display of the content of the main line (option depends on sensor and communication variant)
<ul> <li>Primary value [PV] (default)</li> <li>Main Value [%]</li> <li>Pressure</li> <li>Current [mA] (HART only)</li> <li>Temperature</li> <li>Error number</li> <li>Alternating display</li> </ul>

Damping		
Damping:	 sec (Default 2 sec)	

Smallest calibratable span (preset at factory)  $\rightarrow \square 13$ 

### Level

The following configuration data sheet must be completed and included with the order if the option "F" or "T" has been selected in the Product Configurator, order code for "Calibration; Unit".



1) The conversion factor for the pressure unit is based on a reference temperature of 4 °C (39.2 °F).

2) The conversion factor of the pressure unit refers to a reference temperature of 0  $^{\circ}$ C (32  $^{\circ}$ F).

Dis	play
Disj	play of the content of the main line (option depends on sensor and communication variant)
	Primary value [PV] (default)
	Main Value [%]
	Pressure
	Current [mA] (HART only)
	Temperature
	Level before Lin.
	Tank content
	Error number
	Alternating display

#### Damping

Damping:

sec (Default 2 sec)

HistoROM <sup>®</sup> /M-DAT	The HistoROM®/M-DA 1-5V DC).	AT is a memory module that can be attached to any electronic insert (not for			
	Ordering information:				
	Product Configurator,	order code for "Additional options 1" or Additional options 2", version "N" or			
	as a separate accessory	y (part no.: 52027785).			
Welding flanges and weld-in adapters	For details, refer to TIO	For details, refer to TI00426F/00/EN "Weld-in adapters, process adapters and flanges".			
Manifolds	See the $\rightarrow \blacksquare 78$ .				
	For further details, see	SD01553P/00/EN "Mechanical accessories for pressure measuring devices".			
Additional mechanical accessories		pressure gauge valves, shutoff valves, siphons, condensate pots, cable lapters, mounting brackets, flushing rings, block&bleed valves and protective			
	For details see SD0155	53P/00/EN "Mechanical accessories for pressure measuring devices".			
Service-specific accessories	Accessories	Description			
	DeviceCare SFE100	Configuration tool for HART, PROFIBUS and FOUNDATION Fieldbus field devices Technical Information TI01134S DeviceCare is available for download at www.software-products.endress.com.			
		You need to register in the Endress+Hauser software portal to download the application.			
	FieldCare SFE500	FDT-based plant asset management tool FieldCare can configure all smart field units in your plant and helps you manage them. By using the status information, FieldCare is also a simple but effective way of checking the status and condition of the field devices.			
	Field Xpert SMT70, SMT77	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous (Ex Zone 2) and non-hazardous areas. It is suitable for commissioning and maintenance staff. It manages Endress+Hauser and third-party field instruments with a digital communication interface and documents the progress of the work. The SMT70 is designed as a complete solution. It comes with a pre-installed driver library and is an easy-to-use, touch- enabled tool for managing field devices throughout their entire life cycle. The Field Xpert SMT77 for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1. It is suitable for commissioning and maintenance staff for easy management of field instruments with a digital communication interface. The touch-enabled tablet PC is designed as a complete solution. It comes with comprehensive pre-installed driver libraries and offers users a modern software user interface to manage field instruments throughout the entire life cycle.			

# Accessories

# Supplementary documentation

Field of Activities	Pressure measurement, powerful instruments for process pressure, differential pressure, level and flow:
	FA00004P/00/EN
Technical Information	Cerabar S: TI00383P/00/EN
	<ul> <li>EMC test procedures: TI00241F/00/EN</li> <li>Weld-in adapter, adapter and flanges: TI00426F/00/EN</li> </ul>
Special Documentation	Mechanical accessories for pressure measuring devices: SD01553P/00/EN
Operating Instructions	4 to 20 mA HART: • Cerabar S: BA00271P/00/EN • Description of Device Functions Cerabar S/Deltabar S/Deltapilot S: BA00274P/00/EN
	4 to 20 mA HART with MID parts certificate: BA00412P/00/EN      Description of Device Functions: BA00413P/00/EN
	1-5V DC: Cerabar S PMP71: BA01633P/00/EN
	PROFIBUS PA: • Cerabar S: BA00295P/00/EN • Description of Device Functions Cerabar S/Deltabar S/Deltapilot S: BA00296P/00/EN
	FOUNDATION Fieldbus: • Cerabar S: BA00302P/00/EN
	<ul> <li>Description of Device Functions Cerabar S/Deltabar S/Deltapilot S: BA00303P/00/EN</li> </ul>
Brief Operating Instructions	<ul> <li>4 to 20 mA HART, Cerabar S: KA01019P/00/EN</li> <li>1-5V DC, Cerabar S PMP71: KA01258P/00/EN</li> <li>PROFIBUS PA, Cerabar S: KA01022P/00/EN</li> <li>FOUNDATION Fieldbus, Cerabar S: KA01025P/00/EN</li> </ul>
Functional safety manual (SIL)	Cerabar S (4 to 20 mA): SD00190P/00/EN
Overfill prevention	WHG: ZE00260P/00/DE
Safety Instructions (XA)	Depending on the approval, the following Safety Instructions (XA) are supplied with the device. Th are an integral part of the Operating Instructions.

HART. PROFIBUS PA	FOUNDATION Fieldbus
11111,111011200111	1001101111011110100

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
ATEX II 1/2 G Ex ia IIC T6 Ga/Gb	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00244P	1
ATEX II 1/2 D Ex ta/tb IIIC Da/Db	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	<ul><li>XA00246P</li><li>XA00289P</li></ul>	2
ATEX II 1/2D Ex ia IIIC Da/Db	PMC71	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	<ul><li>XA00247P</li><li>XA00290P</li></ul>	2
ATEX II 1/3D Ex ta/tc IIIC Da/Dc	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	<ul><li>XA00248P</li><li>XA00291P</li></ul>	4
ATEX II 2G Ex d IIC T6 Gb	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00249P	5
ATEX II 2G Ex d ia IIC T6 Gb	PMC71	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00250P	5
ATEX II 1/2G Ex ia IIC T6, WHG (German Water Resources Act)	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00244P	6

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
ATEX II 3 G Ex nA II T6	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00251P	7
ATEX II 1/2G Ex ia IIC T6 Ga/Gb + ATEX II 1/2D Ex ia IIIC Da/Db	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00253P	3
ATEX II 1G Ex ia IIC Ga + II 1D Ex ia IIIC Da	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00276P	8
ATEX II 1/2G Ex ia IIC T6 + II 2G Ex d IIC T6	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00252P	В
ATEX II Ex ia + FM IS + CSA IS ATEX II 1/2G Ex ia IIC T6 + FM/CSA IS Cl.I,II,III Div.1 Gr.A- G, FM/CSA: Zone 0,1,2	PMC71	<ul> <li>4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus</li> <li>HART</li> <li>PROFIBUS PA, FOUNDATION Fieldbus</li> </ul>	<ul> <li>XA00244P</li> <li>XA00593P + XA01059P</li> <li>XA00596P + XA01060P</li> </ul>	E
ATEX II Ex ia / Ex d + FM/CSA IS + XP ATEX II 1/2G Ex ia IIC T6+ ATEX II 2G Ex d IIC T6+ FM/CSA IS + XP CLI.II Div.1 Gr.A-G/B-G FM: Zone 1.2/CSA: Zone 1,2	PMP71, PMP75	<ul> <li>4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus</li> <li>HART</li> <li>PROFIBUS PA, FOUNDATION Fieldbus</li> </ul>	<ul> <li>XA00252P</li> <li>XA00592P + XA01197P</li> <li>XA00590P + XA00590P + XA01198P</li> </ul>	F

# 1) Product Configurator, order code for "Approval"

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
IECEx Ex ia IIC T6 Ga/Gb	PMC71, PMP71, PMP75	4 to 20 mA HART	XB00005P	Ι
IEC Ex d ia IIC T6 Gb	PMC71	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00511P	В
IEC Ex d IIC T6 Gb	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00510P	М

# 1) Product Configurator, order code for "Approval"

# 1-5V DC

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
CSA C/US XP Cl.I Div.1 Gr.B-D, Ex d, Zone 1,2	PMP71	1-5V DC	XA00599P	V

# 1) Product Configurator, order code for "Approval"

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
NEPSI Ex ia IIC T6	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00549P	Н
NEPSI Ex d IIC T6	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00551P	G
NEPSI Ex d ia IIC T6	PMC71	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00551P	G

# 1) Product Configurator, order code for "Approval"

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
JPN Ex d [ia] IIC T6	PMC71	4 to 20 mA HART	TC17436	L
JPN Ex d[ia] IIC T4	PMC71	4 to 20 mA HART	TC17398, TC17399	М
JPN Ex d IIC T6	PMP71 (700 bar version)	4 to 20 mA HART	TC17445	L
JPN Ex d IIC T6	PMP71, PMP75	4 to 20 mA HART	TC17446	L

1) Product Configurator, order code for "Approval"

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
INMETRO Ex ia IIC T6 Ga/Gb	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01315P	J
INMETRO Ex d IIC T6 Gb	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01279P	0
INMETRO Ex ta IIIC Da/Db	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01313P	Z
INMETRO Ex d ia IIC T6 Gb	PMC71	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01280P	Р
INMETRO Ex ia IIIC Da/Db	PMC71	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01314P	Z

1) Product Configurator, order code for "Approval"

# Installation/Control

Directive	Device	Electronics	Documentation	Option <sup>1)</sup>
FM IS Class I, II, III, Division 1, Groups A – G; NI, Class I Division 2, Groups A – D; AEx ia	PMC71, PMP71, PMP75	<ul><li>4 to 20 mA HART</li><li>PROFIBUS PA, FOUNDATION Fieldbus</li></ul>	<ul><li>XA01059P</li><li>XA01060P</li></ul>	S
CSA IS Class I, II, III, Division 1, Groups A – G; Class I Division 2, Groups A – G	PMC71, PMP71, PMP75	<ul><li>4 to 20 mA HART</li><li>PROFIBUS PA, FOUNDATION Fieldbus</li></ul>	<ul><li>XA00593P</li><li>XA00596P</li></ul>	U
FM IS + XP Class I, Division 1, Groups A – D	PMP71, PMP75	<ul><li>4 to 20 mA HART</li><li>PROFIBUS PA, FOUNDATION Fieldbus</li></ul>	• XA01197P • XA01198P	С
CSA IS + XP Class I Division 1, Groups A – D	PMP71, PMP75	<ul><li>4 to 20 mA HART</li><li>PROFIBUS PA, FOUNDATION Fieldbus</li></ul>	<ul><li>XA00592P</li><li>XA00590P</li></ul>	D
FM/CSA IS + XP Class I Division 1, Groups A – D	PMP71, PMP75	<ul> <li>4 to 20 mA HART</li> <li>PROFIBUS PA, FOUNDATION Fieldbus</li> </ul>	<ul> <li>XA00592P + XA01197P</li> <li>XA01198P + XA00590P</li> </ul>	E
FM NI Cl.I Div.2 Groups A - D, Zone 2	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01063P	R
FM XP Cl.I Div.1 Groups A - D, AEx d, Zone 1,2	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01070P	Т
FM DIP Cl.II,III Div.1 Gr.E-G, Zone 21,22	PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	FM3017778	Q
CSA C/US XP Cl.I Div.1 Gr.B-D, Ex d, Zone 1,2	PMC71, PMP71, PMP75	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	ZD00230P + XA00599P	V
CSA C/US General Purpose	PMD75, FMD77, FMD78	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	-	Х

1) Product Configurator, order code for "Approval"



www.addresses.endress.com

