Technical Information **Proline Promag H 300**

Electromagnetic flowmeter



Specialist for hygienic applications with a compact, easily accessible transmitter

Application

- The bidirectional measuring principle is virtually independent of pressure, density, temperature and viscosity
- For applications with sanitary requirements

Device properties

- Liner made of PFA
- Sensor housing made of stainless steel (3-A, EHEDG)
- Wetted materials CIP-/SIP-cleanable
- Compact hygienic dual-compartment housing with IP69 and up to 3 I/Os
- Backlit display with touch control and WLAN access
- Remote display available

Your benefits

- Flexible installation concept numerous hygienic process connections
- Energy-saving flow measurement no pressure loss due to cross section constriction
- Maintenance-free no moving parts
- Full access to process and diagnostic information numerous, freely combinable I/Os and Ethernet
- Reduced complexity and variety freely configurable I/O functionality
- Integrated verification Heartbeat Technology



Table of contents

About this document		Atmosphere	
Symbols	. 4	Relative humidity	
		Operating height	58
Eunstian and system design	5	Degree of protection	58
Function and system design		Vibration- and shock-resistance	58
Measuring principle		Interior cleaning	58
Measuring system		Mechanical load	58
Equipment architecture		Electromagnetic compatibility (EMC)	58
Security	. 7		
		Process	58
Input	. 9		
Measured variable		Medium temperature range	
Measuring range		Conductivity	
Operable flow range		Pressure-temperature ratings	59
Input signal		Pressure tightness	
1 3		Flow limit	65
01	10	Pressure loss	
Output	13	System pressure	
Output and input variants		Vibrations	
Output signal		Magnetism and static electricity	65
Signal on alarm			
Load		Mechanical construction	66
Ex connection data	23	Dimensions in SI units	
Low flow cut off	25	Dimensions in US units	
Galvanic isolation	25	Weight	
Protocol-specific data	25	Measuring tube specification	
		Materials	
Power supply	32	Fitted electrodes	
Terminal assignment	- 1	Process connections	
Available device plugs	33	Surface roughness	
Supply voltage	34	Surface roughness	101
Power consumption	-		
Current consumption		• •	L03
Power supply failure	34	r	103
Overcurrent protection element	-	J J	103
Electrical connection	35	±	103
Terminals	45		104
Cable entries	45		110
Pin assignment, device plug		Network integration	
Cable specification			112
Overvoltage protection		HistoROM data management	113
Overvoltage protection	47		
Deaf and a second and a second	F0	Certificates and approvals	l15
Performance characteristics	50		115
Reference operating conditions	50	UKCA marking	115
Maximum measured error		RCM mark	115
Repeatability	51	Ex approval	115
Temperature measurement response time	52	Sanitary compatibility	116
Influence of ambient temperature	52		116
		Functional safety	116
Installation	52	· · · · · · · · · · · · · · · · · · ·	117
Mounting location			117
Orientation	54		117
Inlet and outlet runs	55		117
Adapters	56	Certification PROFINET	
Special mounting instructions	57		117 117
			117 117
			117 117
Environment	- 1		11 <i>7</i> 118
Ambient temperature range	- 1		118
Storage temperature	57	onici otaniaarao ana garacinico	

2

Ordering information	119
Application packages Diagnostic functionality Heartbeat Technology Cleaning OPC-UA Server	119 119 119 120 120
Accessories	120 122 123
Supplementary documentation Standard documentation Supplementary device-dependent documentation	123
Registered trademarks	125

About this document

Symbols Electrical symbols

Symbol	Meaning
===	Direct current
~	Alternating current
$\overline{}$	Direct current and alternating current
=	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Potential equalization connection (PE: protective earth) Ground terminals that must be connected to ground prior to establishing any other connections.
	The ground terminals are located on the interior and exterior of the device: Interior ground terminal: potential equalization is connected to the supply network. Exterior ground terminal: device is connected to the plant grounding system.

Communication-specific symbols

Symbol	Meaning
	Wireless Local Area Network (WLAN) Communication via a wireless, local network.
•	LED Light emitting diode is off.
<u></u>	LED Light emitting diode is on.
	LED Light emitting diode is flashing.

$Symbols \ for \ certain \ types \ of \ information$

Symbol	Meaning
✓	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
X	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
Ţ <u>i</u>	Reference to documentation
A=	Reference to page
	Reference to graphic
	Visual inspection


Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections
EX	Hazardous area
×	Safe area (non-hazardous area)
≋➡	Flow direction

Function and system design

Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



A002896

- Ue Induced voltage
- B Magnetic induction (magnetic field)
- L Electrode spacing
- I Current
- v Flow velocity

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced (U_e) is proportional to the flow velocity (v) and is supplied to the amplifier by means of two measuring electrodes. The flow volume (Q) is calculated via the pipe cross-section (A). The magnetic field is created through a switched direct current of alternating polarity.

Formulae for calculation

- Induced voltage $U_e = B \cdot L \cdot v$
- Volume flow $Q = A \cdot v$


Measuring system

The device consists of a transmitter and a sensor.

The device is available as a compact version:

The transmitter and sensor form a mechanical unit.

Transmitter




Device versions and materials:

- Transmitter housing
- Aluminum, coated: aluminum, AlSi10Mg, coated
- Stainless, hygienic: stainless steel, 1.4404
- Material of window in transmitter housing:
 - Aluminum, coated: glass
 - Stainless, hygienic: polycarbonate

Configuration:

- External operation via 4-line, illuminated graphic local display (LCD) with touch control and guided menus ("Make-it-run" wizards) for application-specific commissioning.
- Via service interface or WLAN interface:
 - Operating tools (e.g. FieldCare, DeviceCare)
 - Web server (access via Web browser, e.g. Microsoft Internet Explorer, Microsoft Edge)

Sensor




Nominal diameter range: DN 2 to 150 (1/12 to 6")

Materials

- Sensor housing: stainless steel, 1.4301 (304)
- Measuring tubes: stainless steel, 1.4301 (304)
- Liner: PFA
- Electrodes: stainless steel, 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); tantalum; platinum (only up to DN 25 (1"))
- Process connections: stainless steel, 1.4404 (F316L); PVDF; PVC adhesive sleeve
- Seals:
 - DN 2 to 25 (1/12 to 1"): O-ring seal (EPDM, FKM, Kalrez), aseptic gasket seal (EPDM, FKM, silicone)
 - DN 40 to 150 (1 ½ to 6"): aseptic gasket seal (EPDM, FKM, silicone)
- Grounding rings: stainless steel, 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); tantalum

Equipment architecture



 \blacksquare 1 Possibilities for integrating measuring devices into a system

- 1 Control system (e.g. PLC)
- 2 Connecting cable (0/4 to 20 mA HART etc.)
- 3 Fieldbus
- 4 Coupler
- 5 Non-hazardous area
- 6 Hazardous area: Zone 2; Class I, Division 2
- 7 Hazardous area: Zone 1; Class I, Division 1

Security

IT security

Our warranty is valid only if the product is installed and used as described in the Operating Instructions. The product is equipped with security mechanisms to protect it against any inadvertent changes to the settings.

IT security measures, which provide additional protection for the product and associated data transfer, must be implemented by the operators themselves in line with their security standards.

Device-specific IT security

The device offers a range of specific functions to support protective measures on the operator's side. These functions can be configured by the user and guarantee greater in-operation safety if used correctly. An overview of the most important functions is provided in the following section:

Function/interface	Factory setting	Recommendation
Write protection via hardware write protection switch $\Rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $	Not enabled	On an individual basis following risk assessment
Access code (also applies for Web server login or FieldCare connection) → 🖺 8	Not enabled (0000)	Assign a customized access code during commissioning
WLAN (order option in display module)	Enabled	On an individual basis following risk assessment
WLAN security mode	Enabled (WPA2- PSK)	Do not change
WLAN passphrase (password) → 🖺 8	Serial number	Assign a customized WLAN passphrase during commissioning
WLAN mode	Access point	On an individual basis following risk assessment
Web server → 🖺 8	Enabled	On an individual basis following risk assessment
CDI-RJ45 service interface → 🗎 9	-	On an individual basis following risk assessment

Protecting access via hardware write protection

Write access to the parameters of the device via the local display, Web browser or operating tool (e.g. FieldCare, DeviceCare) can be disabled via a write protection switch (DIP switch on the main electronics module). When hardware write protection is enabled, only read access to the parameters is possible.

Hardware write protection is disabled when the device is delivered.

Protecting access via a password

Different passwords are available to protect write access to the device parameters or access to the device via the WLAN interface.

- User-specific access code
 - Protect write access to the device parameters via the local display, Web browser or operating tool (e.g. FieldCare, DeviceCare). Access authorization is clearly regulated through the use of a user-specific access code.
- WLAN passphrase
 - The network key protects a connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface which can be ordered as an option.
- Infrastructure mode
 - When the device is operated in infrastructure mode, the WLAN passphrase corresponds to the WLAN passphrase configured on the operator side.

User-specific access code

Write access to the device parameters via the local display, Web browser or operating tool (e.g. FieldCare, DeviceCare) can be protected by the modifiable, user-specific access code.

WLAN passphrase: Operation as WLAN access point

A connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface, which can be ordered as an optional extra, is protected by the network key. The WLAN authentication of the network key complies with the IEEE 802.11 standard.

When the device is delivered, the network key is pre-defined depending on the device. It can be changed via the **WLAN settings** submenu in the **WLAN passphrase** parameter.

Infrastructure mode

A connection between the device and WLAN access point is protected by means of an SSID and passphrase on the system side. Please contact the relevant system administrator for access.

General notes on the use of passwords

- The access code and network key supplied with the device should be changed during commissioning.
- Follow the general rules for generating a secure password when defining and managing the access code or network key.
- The user is responsible for the management and careful handling of the access code and network key.

Access via Web server

The device can be operated and configured via a Web browser with the integrated Web server. The connection is via the service interface (CDI-RJ45) or the WLAN interface. For device versions with the EtherNet/IP and PROFINET communication protocols, the connection can also be established via the terminal connection for signal transmission with EtherNet/IP, PROFINET (RJ45 plug) or PROFINET with Ethernet-APL (two-wire).

The Web server is enabled when the device is delivered. The Web server can be disabled if necessary (e.g. after commissioning) via the **Web server functionality** parameter.

The device and status information can be hidden on the login page. This prevents unauthorized access to the information.

For detailed information on device parameters, see:

Access via OPC-UA

i

The device can communicate with OPC UA clients using the "OPC UA Server" application package.

The OPC UA server integrated in the device can be accessed via the WLAN access point using the WLAN interface - which can be ordered as an optional extra - or the service interface (CDI- RJ45) via Ethernet network. Access rights and authorization as per separate configuration.

The following Security Modes are supported as per the OPC UA Specification (IEC 62541):

- None
- Basic128Rsa15 signed
- Basic128Rsa15 signed and encrypted

Access via service interface (CDI-RJ45)

The device can be connected to a network via the service interface (CDI-RJ45). Device-specific functions quarantee the secure operation of the device in a network.

The use of relevant industrial standards and guidelines that have been defined by national and international safety committees, such as IEC/ISA62443 or the IEEE, is recommended. This includes organizational security measures such as the assignment of access authorization as well as technical measures such as network segmentation.

- Transmitters with an Ex de approval may not be connected via the service interface (CDI-RJ45)!

 Order code for "Approval transmitter + sensor", options (Ex de): BA, BB, C1, C2, GA, GB, MA, MB, NA, NB
- The device can be incorporated into a ring topology. The device is integrated via the terminal connection for signal transmission (output 1) and the connection to the service interface (CDI-RJ45).

Input

Measured variable

Direct measured variables

- Volume flow (proportional to induced voltage)
- Temperature ¹⁷
- Electrical conductivity

Calculated measured variables

- Mass flow
- Corrected volume flow
- Corrected electrical conductivity ¹⁾

Measuring range

Typically v = 0.01 to 10 m/s (0.03 to 33 ft/s) with the specified accuracy

Flow characteristic values in SI units: DN 2 to 125 ($\frac{1}{12}$ to 5")

Nominal	diameter	Recommended flow	Factory settings		
		min./max. full scale value (v ~ 0.3/10 m/s)	current output		Low flow cut off (v ~ 0.04 m/s)
[mm]	[in]	[dm³/min]	[dm ³ /min] [dm ³] [dm ³ /min]		[dm³/min]
2	1/12	0.06 to 1.8	0.5 0.005 0.01		0.01
4	5/32	0.25 to 7	2 0.025 0.05		0.05
8	5/16	1 to 30	8 0.1 0.1		0.1

¹⁾ Available only for nominal diameters DN 15 to 150 (½ to 6") and with the order code for "Sensor option", option CI "Medium temperature measurement".

Nominal	diameter	Recommended flow	Factory settings		
min./max. full Full scale value current output (v ~ 0.3/10 m/s) (v ~ 2.5 m/s) Pulse value (~ 2 pulse/s)		Low flow cut off (v ~ 0.04 m/s)			
[mm]	[in]	[dm³/min]	[dm³/min]	[dm³]	[dm³/min]
15	1/2	4 to 100	25	0.2	0.5
25 ¹⁾	1	9 to 300	75	0.5	1
40	1 ½	25 to 700	200	1.5	3
50	2	35 to 1100	300	2.5	5
65	-	60 to 2 000	500	5	8
80	3	90 to 3 000	750	5	12
100	4	145 to 4700	1200	10	20
125	5	220 to 7500	1850	15	30

1) The values apply for the product version: 5HxB26

Flow characteristic values in SI units: DN 150 (6")

Nominal	diameter	Recommended flow	Factory settings		
		min./max. full scale value (v ~ 0.3/10 m/s)	current output		Low flow cut off (v ~ 0.04 m/s)
[mm]	[in]	[m³/h]	[m³/h] [m³] [m³/h]		[m³/h]
150	6	20 to 600	150	0.03	2.5

Flow characteristic values in US units: $^{1}\!\!/_{12}$ - 6" (DN 2 - 150)

Nominal	diameter	Recommended flow	Factory settings		
		min./max. full scale value (v ~ 0.3/10 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 2 pulse/s)	Low flow cut off (v ~ 0.04 m/s
[in]	[mm]	[gal/min]	[gal/min]	[gal]	[gal/ min]
1/12	2	0.015 to 0.5	0.1	0.001	0.002
1/32	4	0.07 to 2	0.5	0.005	0.008
5/16	8	0.25 to 8	2	0.02	0.025
1/2	15	1 to 27	6	0.05	0.1
1 ¹⁾	25	2.5 to 80	18	0.2	0.25
1 1/2	40	7 to 190	50	0.5	0.75
2	50	10 to 300	75	0.5	1.25
3	80	24 to 800	200	2	2.5
4	100	40 to 1250	300	2	4
5	125	60 to 1950	450	5	7
6	150	90 to 2 650	600	5	12

1) The values apply for the product version: 5HxB26

Recommended measuring range

Flow limit → 🖺 65

For custody transfer, the applicable approval determines the permitted measuring range, the pulse value and the low flow cut off.

Operable flow range

Over 1000:1

For custody transfer, the operable flow range is 100 : 1 to 630 : 1, depending on the nominal diameter. Further details are specified by the applicable approval.

Input signal

Output and input variants

→ 🖺 13

External measured values

To increase the accuracy of certain measured variables or to calculate the mass flow, the automation system can continuously write different measured values to the measuring device:

- Medium temperature enables temperature-compensated conductivity measurement (e.g. iTEMP)
- Reference density for calculating the mass flow

It is recommended to read in external measured values to calculate the corrected volume flow.

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Current input

Digital communication

The measured values can be written by the automation system via:

- FOUNDATION Fieldbus
- PROFIBUS DP
- PROFIBUS PA
- Modbus RS485
- EtherNet/IP
- PROFINET
- PROFINET with Ethernet-APL

Current input 0/4 to 20 mA

Current input	0/4 to 20 mA (active/passive)	
Current span	4 to 20 mA (active)0/4 to 20 mA (passive)	
Resolution	1 μΑ	
Voltage drop	Typically: 0.6 to 2 V for 3.6 to 22 mA (passive)	
Maximum input voltage	≤ 30 V (passive)	
Open-circuit voltage	≤ 28.8 V (active)	
Possible input variables	TemperatureDensity	

Status input

Maximum input values	■ DC -3 to 30 V ■ If status input is active (ON): $R_i > 3$ k Ω
Response time	Configurable: 5 to 200 ms
Input signal level	 Low signal: DC -3 to +5 V High signal: DC 12 to 30 V
Assignable functions	 Off Reset the individual totalizers separately Reset all totalizers Flow override

Output

Output and input variants

Depending on the option selected for output/input 1, different options are available for the other outputs and inputs. Only one option can be selected for each output/input 1 to 3. The following tables must be read vertically (\downarrow) .

Example: If the option BA "4-20 mA HART" was selected for output/input 1, one of the options A, B, D, E, F, H, I or J is available for output 2 and one of the options A, B, D, E, F, H, I or J is available for output 3.

Output/input 1 and options for output/input 2



Options for output/input $3 \rightarrow 14$

Order code for "Output; input 1" (020) →	Possible options												
Current output 4 to 20 mA HART	ВА												
Current output 4 to 20 mA HART Ex i passive	4	CA											
Current output 4 to 20 mA HART Ex i active		\	СС										
FOUNDATION Fieldbus			1	SA									
FOUNDATION Fieldbus Ex i				4	TA								
PROFIBUS DP					4	LA							
PROFIBUS PA						4	GA						
PROFIBUS PA Ex i							4	НА					
Modbus RS485								4	MA				
EtherNet/IP 2-port switch integrated									4	NA			
PROFINET 2-port switch integrated										\	RA		
PROFINET with Ethernet-APL											\	RB	
PROFINET with Ethernet-APL Ex i												1	RC
Order code for "Output; input 2" (021) →	\	\	\	4	\	4	1	4	4	\rightarrow	\	1	\
Not assigned	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α
Current output 4 to 20 mA	В			В		В	В		В	В	В	В	
Current output 4 to 20 mA Ex i passive		С	С		С			С					С
User-configurable input/output 1)	D			D		D	D		D	D	D	D	
Pulse/frequency/switch output	E			Е		Е	Е		Е	E	E	Е	
Double pulse output ²⁾	F								F				
Pulse/frequency/switch output Ex i passive		G	G		G			G					G
Relay output	Н			Н		Н	Н		Н	Н	Н	Н	
Current input 0/4 to 20 mA	I			I		I	I		I	I	I	I	
Status input	ī			ı		J	J		J	J	J	J	

²⁾ If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for selection for output/input 3 (022).

Output/input 1 and options for output/input 3

Options for output/input $2 \rightarrow 2$ 13

Order code for "Output; input 1" (020) \rightarrow	Possible options												
Current output 4 to 20 mA HART	ВА												
Current output 4 to 20 mA HART Ex i passive	4	CA											
Current output 4 to 20 mA HART Ex i active		4	CC										
FOUNDATION Fieldbus			4	SA									
FOUNDATION Fieldbus Ex i				4	TA								
PROFIBUS DP					4	LA							
PROFIBUS PA						4	GA						
PROFIBUS PA Ex i							4	НА					
Modbus RS485								\	MA				
EtherNet/IP 2-port switch integrated									4	NA			
PROFINET 2-port switch integrated										→	RA		
PROFINET with Ethernet-APL											1	RB	
PROFINET with Ethernet-APL Ex i												4	RC
Order code for "Output; input 3" (022) →	4	4	4	4	4	4	4	4	4	→	4	4	+
Not assigned	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α
Current output 4 to 20 mA	В					В			В	В	В	В	
Current output 4 to 20 mA Ex i passive		С	С										
User-configurable input/output	D					D			D	D	D	D	
Pulse/frequency/switch output	Е					E			Е	Е	Е	Е	
Double pulse output (slave) 1)	F								F				
Pulse/frequency/switch output Ex i passive		G	G										
Relay output	Н					Н			Н	Н	Н	Н	
Current input 0/4 to 20 mA	I					I			I	I	I	I	
Status input	J					J			J	J	J	J	

¹⁾ If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for output/input 3 (022).

Output signal

Current output 4 to 20 mA HART

Order code	"Output; input 1" (20): Option BA: current output 4 to 20 mA HART
Signal mode	Can be set to: Active Passive
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	250 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature

Current output 4 to 20 mA HART Ex i

Order code	"Output; input 1" (20) choose from: Option CA: current output 4 to 20 mA HART Ex i passive Option CC: current output 4 to 20 mA HART Ex i active
Signal mode	Depends on the selected order version.
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current
Open-circuit voltage	DC 21.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	 250 to 400 Ω (active) 250 to 700 Ω (passive)
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature

FOUNDATION Fieldbus

FOUNDATION Fieldbus	H1, IEC 61158-2, galvanically isolated
Data transfer	31.25 kbit/s
Current consumption	10 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud
Terminating resistor	Integrated, can be activated via DIP switches

PROFIBUS PA

PROFIBUS PA	In accordance with EN 50170 Volume 2, IEC 61158-2 (MBP), galvanically isolated
Data transmission	31.25 kbit/s
Current consumption	10 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

Modbus RS485

Physical interface	RS485 in accordance with EIA/TIA-485 standard
Terminating resistor	Integrated, can be activated via DIP switches

EtherNet/IP

Standards In accordance with	IEEE 802.3
------------------------------	------------

PROFINET

Standards	In accordance with IEEE 802.3
-----------	-------------------------------

PROFINET with Ethernet-APL

Device use	Device connection to an APL field switch
	The device may only be operated according to the following APL port
	classifications:
	If used in hazardous areas: SLAA or SLAC 1) K. A.
	If used in non-hazardous areas: SLAX
	Connection values of APL field switch (corresponds to APL port classification SPCC or SPAA, for instance):
	 Maximum input voltage: 15 V_{DC} Minimum output values: 0.54 W
	Device connection to an SPE switch
	The device may only be operated according to the following PoDL power class: If used in the non-hazardous area: PoDL power class 10
	Connection values of SPE switch (corresponds to PoDL power class 10, 11 or 12): • Maximum input voltage: 30 V _{DC} • Minimum output values: 1.85 W
PROFINET	According to IEC 61158 and IEC 61784
Ethernet-APL	According to IEEE 802.3cg, APL port profile specification v1.0, galvanically isolated
Data transfer	10 Mbit/s
Current consumption	Transmitter
•	■ Max. 400 mA(24 V)
	■ Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)
Permitted supply voltage	9 to 30 V
Network connection	With integrated reverse polarity protection

1) For more information on using the device in the hazardous area, see the Ex-specific Safety Instructions

Current output 4 to 20 mA

Order code	"Output; input 2" (21), "Output; input 3" (022): Option B: current output 4 to 20 mA
Signal mode	Can be set to: Active Passive
Current span	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA 1 to 20 mA (only if the signal mode is active) Fixed current
Maximum output values	22.5 mA
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature

Current output 4 to 20 mA Ex i passive

Order code	"Output; input 2" (21), "Output; input 3" (022): Option C: current output 4 to 20 mA Ex i passive
Signal mode	Passive
Current span	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA Fixed current
Maximum output values	22.5 mA
Maximum input voltage	DC 30 V
Load	0 to 700Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature

Pulse/frequency/switch output

Function	Can be configured as pulse, frequency or switch output
Version	Open collector Can be set to: Active Passive Passive NAMUR Ex-i, passive
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Voltage drop	For 22.5 mA: ≤ DC 2 V
Pulse output	
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Pulse width	Configurable: 0.05 to 2 000 ms
Maximum pulse rate	10 000 Impulse/s
Pulse value	Configurable
Assignable measured variables	Volume flowMass flowCorrected volume flow
Frequency output	
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Output frequency	Configurable: end value frequency 2 to 10 000 Hz(f $_{ m max}$ = 12 500 Hz)

Damping	Configurable: 0 to 999.9 s
Pulse/pause ratio	1:1
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature
Switch output	
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Switching behavior	Binary, conductive or non-conductive
Switching delay	Configurable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	 Off On Diagnostic behavior Limit value: Off Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Totalizer 1-3 Temperature Electronics temperature Flow direction monitoring Status Empty pipe detection Buildup index HBSI limit value exceeded Low flow cut off

Double pulse output

Function	Double pulse
Version	Open collector
	Can be set to: Active Passive Passive NAMUR
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Voltage drop	For 22.5 mA: ≤ DC 2 V
Output frequency	Configurable: 0 to 1000 Hz
Damping	Configurable: 0 to 999 s

Pulse/pause ratio	1:1
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature

Relay output

Function	Switch output
Version	Relay output, galvanically isolated
Switching behavior	Can be set to: NO (normally open), factory setting NC (normally closed)
Maximum switching capacity (passive)	■ DC 30 V, 0.1 A ■ AC 30 V, 0.5 A
Assignable functions	 Off On Diagnostic behavior Limit value: Off Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Totalizer 1-3 Temperature Electronics temperature Flow direction monitoring Status Empty pipe detection Buildup index HBSI limit value exceeded Low flow cut off

$User-configurable\ input/output$

 $\textbf{One} \ specific input or output is assigned to a user-configurable input/output (configurable I/O) during device commissioning.$

The following inputs and outputs are available for assignment:

- Choice of current output: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Pulse/frequency/switch output
- Choice of current input: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Status input

The technical values correspond to those of the inputs and outputs described in this section.

Signal on alarm

Depending on the interface, failure information is displayed as follows:

HART current output

Device diagnostics	Device condition can be read out via HART Command 48
--------------------	--

PROFIBUS PA

Status and alarm messages	Diagnostics in accordance with PROFIBUS PA Profile 3.02
Failure current FDE (Fault Disconnection Electronic)	0 mA

PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

EtherNet/IP

Device diagnostics	Device condition can be read out in Input Assembly
--------------------	--

PROFINET

Device diagnostics	According to "Application Layer protocol for decentralized periphery", Version 2.3	l
--------------------	--	---

PROFINET with Ethernet-APL

Device diagnostics	Diagnostics according to PROFINET PA Profile 4
--------------------	--

FOUNDATION Fieldbus

Status and alarm messages	Diagnostics in accordance with FF-891
Failure current FDE (Fault Disconnection Electronic)	0 mA

Modbus RS485

Failure mode Choose from:			
	 NaN value instead of current value 		
	■ Last valid value		

Current output 0/4 to 20 mA

4 to 20 mA

Choose from: 4 to 20 mA in accordance with NAMUR recommendation NE 43 4 to 20 mA in accordance with US Min. value: 3.59 mA Max. value: 22.5 mA Freely definable value between: 3.59 to 22.5 mA Actual value
Last value

0 to 20 mA

Failure mode	Choose from:		
	■ Maximum alarm: 22 mA		
	■ Freely definable value between: 0 to 20.5 mA		

Pulse/frequency/switch output

Pulse output		
Failure mode	Choose from: Actual value No pulses	
Frequency output		
Failure mode	Choose from: Actual value O Hz Defined value (f max 2 to 12 500 Hz)	
Switch output		
Failure mode	Choose from: Current status Open Closed	

Relay output

Failure mode	Choose from:
	Current status
	■ Open
	■ Closed

Local display

Plain text display	With information on cause and remedial measures
Backlight	Red backlighting indicates a device error.




Status signal as per NAMUR recommendation NE 107

Interface/protocol

- Via digital communication:
 - HART protocol
 - FOUNDATION Fieldbus
 - PROFIBUS PA
 - PROFIBUS DP
 - Modbus RS485
 - EtherNet/IP
 - PROFINET
 - PROFINET with Ethernet-APL
- Via service interface
 - CDI-RJ45 service interface
 - WLAN interface

Plain text display	With information on cause and remedial measures
--------------------	---



Web browser

Plain text display	With information on cause and remedial measures

Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes		
	The following information is displayed depending on the device version:		
	 Supply voltage active 		
	Data transmission active		
	Device alarm/error has occurred		
	 EtherNet/IP network available 		
	■ EtherNet/IP connection established		
	PROFINET network available		
	 PROFINET connection established 		
	PROFINET blinking feature		

Load

Output signal → 🖺 15

Ex connection data

Safety-related values

Order code for "Output; input 1"	Output type	Safety-related values "Output; input 1"	
		26 (+)	27 (-)
Option BA	Current output 4 to 20 mA HART	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option GA	PROFIBUS PA	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option LA	PROFIBUS DP	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option MA	Modbus RS485	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option SA	FOUNDATION Fieldbus	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option NA	EtherNet/IP	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option RA	PROFINET	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option RB	PROFINET with Ethernet- APL	$ \begin{array}{c} \text{APL port profile SLAX} \\ \text{SPE PoDL classes 10, 11, 12} \\ U_{N} = 30 \ V_{DC} \\ U_{M} = 250 \ V_{AC} \\ \end{array} $	2

Order code for	Output type	Safety-related values			
"Output; input 2"; "Output; input 3"		Output;	input 2	Output;	input 3
• / •		24 (+)	25 (-)	22 (+)	23 (-)
Option B	Current output 4 to 20 mA	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm AC}$			
Option D	User-configurable input/ output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm AC}$			
Option E	Pulse/frequency/switch output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm AC}$			
Option F	Double pulse output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm AC}$	2		
Option H	Relay output	$U_{N} = 30 V_{DC}$ $I_{N} = 100 \text{ mA}_{DC}$ $U_{M} = 250 V_{AC}$			

Order code for	Output type	Safety-related values			
"Output; input 2"; "Output; input 3"		Output; input 2 Output; inpu		input 3	
		24 (+)	25 (-)	22 (+)	23 (-)
Option I	Current input 4 to 20 mA	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	2		
Option J	Status input	$U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$			

Intrinsically safe values

Order code "Output; input 1"	Output type	Intrinsically safe values "Output; input 1"		
		26 (+)	27 (-)	
Option CA	Current output 4 to 20 mA HART Ex i passive	$\begin{split} &U_{i} = 30 \text{ V} \\ &I_{i} = 100 \text{ mA} \\ &P_{i} = 1.25 \text{ W} \\ &L_{i} = 0 \mu\text{H} \\ &C_{i} = 6 \text{ nF} \end{split}$		
Option CC	Current output 4 to 20 mA HART Ex i active	Ex ia $^{1)}$ $U_0 = 21.8 \text{ V}$ $I_0 = 90 \text{ mA}$ $P_0 = 491 \text{ mW}$ $L_0 = 4.1 \text{ mH (IIC)/15 mH (IIB)}$ $C_0 = 160 \text{ nF (IIC)/}$ 1 160 nF (IIB)	Ex ic $^{2)}$ $U_0 = 21.8 \text{ V}$ $l_0 = 90 \text{ mA}$ $P_0 = 491 \text{ mW}$ $L_0 = 9 \text{ mH (IIC)/39 mH (IIB)}$ $C_0 = 600 \text{ nF (IIC)/4000 nF (IIB)}$	
		$U_i = 30 \text{ V}$ $l_i = 10 \text{ mA}$ $P_i = 0.3 \text{ W}$ $L_i = 5 \mu\text{H}$ $C_i = 6 \text{ nF}$		
Option HA	PROFIBUS PA Ex i (FISCO Field Device)	$\begin{array}{llllllllllllllllllllllllllllllllllll$		
Option TA	FOUNDATION Fieldbus Ex i	$\begin{array}{llllllllllllllllllllllllllllllllllll$		
Option RC	PROFINET with Ethernet-APL Ex i	Ex ia ¹⁾ 2-WISE power load APL port profile SLAA Ex ic ²⁾ 2-WISE power load APL port profile SLAC		

¹⁾ 2) Only available for Proline 500 transmitter Zone 1; Class I, Division 1. Only available for transmitter Zone 2; Class I, Division 2.

Order code for	Output type	Intrinsically safe values or NIFW values			values
"Output; input 2"; "Output; input 3"		Output;	input 2	Output;	input 3
• / •		24 (+)	25 (-)	22 (+)	23 (-)
Option C	Current output 4 to 20 mA Ex i passive	$\begin{aligned} &U_{i} = 30 \text{ V} \\ &l_{i} = 100 \text{ mA} \\ &P_{i} = 1.25 \text{ W} \\ &L_{i} = 0 \\ &C_{i} = 0 \end{aligned}$			
Option G	Pulse/frequency/switch output Ex i passive	$U_{i} = 30 \text{ V}$ $l_{i} = 100 \text{ mA}$ $P_{i} = 1.25 \text{ W}$ $L_{i} = 0$ $C_{i} = 0$			

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

The outputs are galvanically isolated:

- from the power supply
- from one another
- $\ \ \, \blacksquare$ from the potential equalization (PE) terminal

Protocol-specific data

HART

Manufacturer ID	0x11
Device type ID	0x3C
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω
System integration	Information on system integration: Operating Instructions → 🗎 124. ■ Measured variables via HART protocol ■ Burst Mode functionality

FOUNDATION Fieldbus

Manufacturer ID	0x452B48 (hex)
Ident number	0x103C (hex)
Device revision	1
DD revision	Information and files under:
CFF revision	www.endress.comwww.fieldcommgroup.org
Interoperability Test Kit (ITK)	Version 6.2.0
ITK Test Campaign Number	Information: www.endress.com www.fieldcommgroup.org
Link Master capability (LAS)	Yes
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device
Node address	Factory setting: 247 (0xF7)

Supported functions	The following methods are supported: Restart ENP Restart Diagnostic Set to OOS Set to AUTO Read trend data Read event logbook
Virtual Communication Relation	onships (VCRs)
Number of VCRs	44
Number of link objects in VFD	50
Permanent entries	1
Client VCRs	0
Server VCRs	10
Source VCRs	43
Sink VCRs	0
Subscriber VCRs	43
Publisher VCRs	43
Device Link Capabilities	
Slot time	4
Min. delay between PDU	8
Max. response delay	16
System integration	Information regarding system integration: Operating Instructions → 🖺 124. Cyclic data transmission Description of the modules Execution times Methods

PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x1570
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: ■ https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ https://www.profibus.com
Supported functions	Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Via operating tools (e.g. FieldCare)

Compatibility with earlier model	If the device is replaced, the measuring device Promag 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promag 300 GSD file.
	Earlier models: Promag 50 PROFIBUS DP ID No.: 1546 (hex) Extended GSD file: EH3x1546.gsd Standard GSD file: EH3_1546.gsd Promag 53 PROFIBUS DP ID No.: 1526 (hex) Extended GSD file: EH3x1526.gsd Standard GSD file: EH3x1526.gsd
	Description of the function scope of compatibility: Operating Instructions $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $
System integration	Information regarding system integration: Operating Instructions $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $
	 Cyclic data transmission Block model Description of the modules

PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x156C
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: ■ https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ https://www.profibus.com
Supported functions	 Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Local display Via operating tools (e.g. FieldCare)
Compatibility with earlier model	If the device is replaced, the measuring device Promag 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promag 300 GSD file. Earlier models: Promag 50 PROFIBUS PA ID No.: 1525 (hex) Extended GSD file: EH3x1525.gsd Standard GSD file: EH3_1525.gsd Promag 53 PROFIBUS PA ID No.: 1527 (hex) Extended GSD file: EH3x1527.gsd Standard GSD file: EH3_1527.gsd Description of the function scope of compatibility: Operating Instructions → 124.
System integration	Information regarding system integration: Operating Instructions → 🗎 124. Cyclic data transmission Block model Description of the modules

Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1
Response times	 Direct data access: typically 25 to 50 ms Auto-scan buffer (data range): typically 3 to 5 ms
Device type	Slave
Slave address range	1 to 247
Broadcast address range	0
Function codes	 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers
Broadcast messages	Supported by the following function codes: • 06: Write single registers • 16: Write multiple registers • 23: Read/write multiple registers
Supported baud rate	■ 1200 BAUD ■ 2400 BAUD ■ 4800 BAUD ■ 9600 BAUD ■ 19200 BAUD ■ 38400 BAUD ■ 57600 BAUD ■ 115200 BAUD
Data transfer mode	■ ASCII ■ RTU
Data access	Each device parameter can be accessed via Modbus RS485. For Modbus register information
Compatibility with earlier model	If the device is replaced, the measuring device Promag 300 supports the compatibility of the Modbus registers for the process variables and the diagnostic information with the previous model Promag 53. It is not necessary to change the engineering parameters in the automation system. □ Description of the function scope of compatibility: Operating Instructions → □ 124.
System integration	Information on system integration: Operating Instructions → 🖺 124. ■ Modbus RS485 information ■ Function codes ■ Register information ■ Response time ■ Modbus data map

EtherNet/IP

Protocol	 The CIP Networks Library Volume 1: Common Industrial Protocol The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP
Communication type	■ 10Base-T ■ 100Base-TX
Device profile	Generic device (product type: 0x2B)
Manufacturer ID	0x000049E
Device type ID	0x103C
Baud rates	Automatic 10/100 Mbit with half-duplex and full-duplex detection
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Supported CIP connections	Max. 3 connections

Explicit connections	Max. 6 connections
I/O connections	Max. 6 connections (scanner)
Configuration options for measuring device	 DIP switches on the electronics module for IP addressing Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser Electronic Data Sheet (EDS) integrated in the measuring device
Configuration of the EtherNet interface	 Speed: 10 MBit, 100 MBit, auto (factory setting) Duplex: half-duplex, full-duplex, auto (factory setting)
Configuration of the device address	 DIP switches on the electronics module for IP addressing (last octet) DHCP Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser EtherNet/IP tools, e.g. RSLinx (Rockwell Automation)
Device Level Ring (DLR)	Yes
System integration	Information regarding system integration: Operating Instructions → □ 124.
	 Cyclic data transmission Block model Input and output groups

PROFINET

	I					
Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.3					
Communication type	100 MBit/s					
Conformance Class	Conformance Class B					
Netload Class	Netload Class 2 0 Mbps					
Baud rates	Automatic 100 Mbit/s with full-duplex detection					
Cycle times	From 8 ms					
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs					
Media Redundancy Protocol (MRP)	Yes					
System redundancy support	System redundancy S2 (2 AR with 1 NAP)					
Device profile	Application interface identifier 0xF600 Generic device					
Manufacturer ID	0x11					
Device type ID	0x843C					
Device description files (GSD, DTM, DD)	Information and files under: ■ www.endress.com On the product page for the device: Documents/Software → Device drivers ■ www.profibus.com					
Supported connections	 2 x AR (IO Controller AR) 1 x AR (IO-Supervisor Device AR connection allowed) 1 x Input CR (Communication Relation) 1 x Output CR (Communication Relation) 1 x Alarm CR (Communication Relation) 					
Configuration options for measuring device	 DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device. Onsite operation 					

Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server
Supported functions	 Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM)
System integration	Information regarding system integration: Operating Instructions → 🖺 124. Cyclic data transmission Overview and description of the modules Status coding Startup configuration Factory setting

PROFINET with Ethernet-APL

Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.4
Communication type	Ethernet Advanced Physical Layer 10BASE-T1L
Conformance Class	Conformance Class B (PA)
Netload Class	Netload Class 2 0 Mbps
Baud rates	10 Mbit/s Full-duplex
Cycle times	64 ms
Polarity	Automatic correction of crossed "APL signal +" and "APL signal -" signal lines
Media Redundancy Protocol (MRP)	Not possible (point-to-point connection to APL field switch)
System redundancy support	System redundancy S2 (2 AR with 1 NAP)
Device profile	PROFINET PA profile 4 (Application interface identifier API: 0x9700)
Manufacturer ID	0x11
Device type ID	0xA43C
Device description files (GSD, DTM, FDI)	Information and files under: ■ www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ www.profibus.com
Supported connections	 2x AR (IO Controller AR) 2x AR (IO Supervisor Device AR connection allowed)
Configuration options for measuring device	 DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device. Onsite operation
Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server

Supported functions	 Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM with FDI package)
System integration	Information regarding system integration: Operating Instructions → 🗎 124. Cyclic data transmission Overview and description of the modules Status coding Startup configuration Factory setting

Power supply

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

Supply voltage		Input/output 1		Input/output 2		Input/output 3		
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)	
		The terminal assignment depends on the specific device version ordered → 🖺 13.						

FOUNDATION Fieldbus

Supply voltage		Supply voltage Input/output 1		Input/output 2		Input/output 3			
1 (+)	2 (-)	26 (A)	27 (B)	24 (+)	25 (-)	22 (+)	23 (-)		
		The termina	The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $						

PROFIBUS DP

Supply voltage		Input/output 1		Input/output 2		Input/output 3		
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	
		The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $						

PROFIBUS PA

Supply voltage		Input/output 1		Input/output 2		Input/output 3			
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)		
		The termina	The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $						

Modbus RS485

Supply voltage		Input/output 1		Input/output 2		Input/output 3		
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)	
		The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $						

PROFINET

Supply	Supply voltage Input/output 1		Input/output 2		Input/output 3	
1 (+)	2 (-)	PROFINET (RJ45 connector)		3	22 (+) t depends on t rdered → 🗎 1	*

PROFINET with Ethernet-APL

Supply voltage		Input/output 1	Input/output 2		Input/output 3	
1 (+)	2 (-)	PROFINET	24 (+)	25 (-)	22 (+)	23 (-)
		(RJ45 connector)			t depends on t rdered → 🖺 1	

EtherNet/IP

Supply	y voltage	Input/output 1	Input/output 2		Input/output 3	
1 (+)	2 (-)	EtherNet/IP	24 (+)	25 (-)	22 (+)	23 (-)
		(RJ45 connector)			t depends on t rdered → 🖺 1	*

Available device plugs

Povice plugs may not be used in hazardous areas!

Device plugs for fieldbus systems:

Order code for "Input; output 1"

- Option SA "FOUNDATION Fieldbus" →

 ③ 33
- Option **GA** "PROFIBUS PA" → 🖺 33
- Option **NA** "EtherNet/IP" → 🖺 33
- Option **RA** "PROFINET" → 🗎 34
- Option **RB** "PROFINET with Ethernet-APL" → 🖺 34

Device plug for connecting to the service interface:

Order code for "Accessory mounted"

Option NB, adapter RJ45 M12 (service interface) →

46

Order code for "Input; output 1", option SA "FOUNDATION Fieldbus"

Order code for	Cable entry/connection → 🗎 35	
"Electrical connection"	2 3	
M, 3, 4, 5	7/8" connector	-

Order code for "Input; output 1", option GA "PROFIBUS PA"

Order code for	Cable entry/connection → 🖺 35		
"Electrical connection"	2	3	
L, N, P, U	Connector M12 × 1	-	

Order code for "Input; output 1", option NA "EtherNet/IP"

Order code for	Cable entry/connection → 🖺 35		
"Electrical connection"	2	3	
L, N, P, U	Connector M12 × 1	-	
R ¹⁾²⁾ , S ¹⁾²⁾ , T ¹⁾²⁾ , V ¹⁾²⁾	Connector M12 × 1	Connector M12 × 1	

Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001

2) Suitable for integrating the device in a ring topology.

Order code for "Input; output 1", option RA "PROFINET"

Order code for	Cable entry/connection → 🖺 35		
"Electrical connection"	2	3	
L, N, P, U	Connector M12 × 1	-	
R ^{1) 2)} , S ^{1) 2)} , T ^{1) 2)} , V ^{1) 2)}	Connector M12 × 1	Connector M12 × 1	

- Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001.
- 2) Suitable for integrating the device in a ring topology.

Order code for "Input; output 1", option RB "PROFINET with Ethernet-APL"

Order code	Cable entry/connection → 🖺 35		
"Electrical connection"	2	3	
L, N, P, U	M12 plug × 1	-	

Order code for "Accessory mounted", option NB "Adapter RJ45 M12 (service interface)"

Order code	Cable entry/coupling → 🖺 35		
"Accessory mounted"	Cable entry 2	Cable entry 3	
NB	Plug M12 × 1	-	

Supply voltage

Order code for "Power supply"	Terminal voltage		Frequency range
Option D	DC 24 V	±20%	-
Option E	AC 100 to 240 V	-15 to +10%	50/60 Hz, ±4 Hz
Option I	DC 24 V	±20%	-
Option I	AC 100 to 240 V	-15 to +10%	50/60 Hz, ±4 Hz

Power consumption

Transmitter

Max. 10 W (active power)

switch-on current Max. 36 A (<5 ms) as per NAMUR Recommendation NE 21	
---	--

Current consumption

Transmitter

- Max. 400 mA (24 V)
- Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)

Power supply failure

- Totalizers stop at the last value measured.
- Depending on the device version, the configuration is retained in the device memoryor in the pluggable data memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

Overcurrent protection element

The device must be operated with a dedicated circuit breaker, as it does not have an ON/OFF switch of its own.


- The circuit breaker must be easy to reach and labeled accordingly.
- Permitted nominal current of the circuit breaker: 2 A up to maximum 10 A.

Electrical connection

Transmitter connection



- Terminal assignment → 🖺 32
- Device plugs available → 🗎 33



- Terminal connection for supply voltage
- Terminal connection for signal transmission, input/output 2
- Terminal connection for signal transmission, input/output or terminal for network connection via service interface (CDI-RJ45); Optional: terminal connection for external WLAN antenna or connection for remote display and operating module DKX001
- Terminal connection for potential equalization (PE)
- An adapter for the RJ45 to the M12 plug is optionally available: Order code for "Accessories", option NB: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can therefore be established via an M12 plug without opening the device.

Network connection via service interface (CDI-RJ45) \rightarrow \blacksquare 110


Connecting in a ring topology

Device versions with EtherNet/IP and PROFINET communication protocols can be integrated into a ring topology. The device is integrated via the terminal connection for signal transmission (output 1) and the connection to the service interface (CDI-RJ45).



Integrate the transmitter into a ring topology:

- EtherNet/IP
 - PROFINET




- Terminal connection for supply voltage
- Terminal connection for signal transmission: PROFINET or EtherNet/IP (RJ45 connector) 2
- *Terminal connection to service interface (CDI-RJ45)*
- Terminal connection for potential equalization (PE)

If the device has additional inputs/outputs, these are routed in parallel via the cable entry for connection to the service interface (CDI-RJ45).

Connecting the remote display and operating module DKX001

- i
- The remote display and operating module DKX001 is available as an optional extra $\rightarrow \triangleq 120$.
- The remote display and operating module DKX001 is only available for the following housing version: order code for "Housing": option A "Aluminum, coated"
- The measuring device is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring device. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring device display module. Only one display or operation unit may be connected to the transmitter at any one time.




A002751

- 1 Remote display and operating module DKX001
- 2 Terminal connection for potential equalization (PE)
- 3 Connecting cable
- 4 Measuring device
- 5 Terminal connection for potential equalization (PE)


Connection examples

Current output 4 to 20 mA HART




A0029055

- 2 Connection example for 4 to 20 mA HART current output (active)
- 1 Automation system with current input (e.g. PLC)
- 3 Connection for HART operating devices → В 104
- 5 Analog display unit: observe maximum load → 🖺 15
- 6 Transmitter



- \blacksquare 3 Connection example for 4 to 20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications → 🖺 47
- 5 Transmitter


HART input



■ 4 Connection example for HART input with a common negative (passive)

- 1 Automation system with HART output (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 Analog display unit: observe maximum load → 🖺 15
- Pressure transmitter (e.g. Cerabar M, Cerabar S): see requirements
- 6 Transmitter


PROFIBUS PA



A00287

- 5 Connection example for PROFIBUS PA
- 1 Control system (e.g. PLC)
- 2 PROFIBUS PA segment coupler
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line


PROFIBUS DP



- \blacksquare 6 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2
- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter
- If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.


38

EtherNet/IP




- 7 Connection example for EtherNet/IP
- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter

EtherNet/IP: DLR (Device Level Ring)



- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 4 Transmitter
- 5 Connecting cable between the two transmitters


PROFINET



 \blacksquare 8 Connection example for PROFINET


- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter

PROFINET with Ethernet-APL



- **9** ${\it Connection example for PROFINET with Ethernet-APL}$
- 1 Cable shield
- 2 Measuring device
- 3 Local grounding
- Potential equalization
 Trunk or TCP
- 5
- Field switch

PROFINET: MRP (Media Redundancy Protocol)




A0027544

- Control system (e.g. PLC) Ethernet switch
- 2
- 3 *Observe cable specifications* \rightarrow \blacksquare 47
- Transmitter 4
- ${\it Connecting\ cable\ between\ the\ two\ transmitters}$

40


PROFINET: system redundancy S2



■ 10 Connection example for system redundancy S2

- Control system 1 (e.g. PLC)
- Synchronization of control systems 2
- Control system 2 (e.g. PLC)
- Industrial Ethernet Managed Switch 4
- Transmitter


FOUNDATION Fieldbus



■ 11 Connection example for FOUNDATION Fieldbus

- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus) 2
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- T-box
- Measuring device
- Local grounding 6
- Bus terminator
- Potential matching line


Modbus RS485



 \blacksquare 12 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter


Current output 4-20 mA



A00287

■ 13 Connection example for 4-20 mA current output (active)

- 1 Automation system with current input (e.g. PLC)
- 2 Analog display unit: observe maximum load $\rightarrow \square$ 15
- 3 Transmitter




A0028759

■ 14 Connection example for 4-20 mA current output (passive)


- 1 Automation system with current input (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Analog display unit: observe maximum load $\rightarrow \blacksquare 15$
- 4 Transmitter

Pulse/frequency output



- 15 Connection example for pulse/frequency output (passive)
- Automation system with pulse/frequency input (e.g. PLC with 10 kΩ pull-up or pull-down resistor)
- 2 Power supply
- *3* Transmitter: observe input values → 🖺 18


Switch output



■ 16 Connection example for switch output (passive)


- Automation system with switch input (e.g. PLC with a 10 kΩ pull-up or pull-down resistor)
- 2 Power supply

Double pulse output



■ 17 Connection example for double pulse output (active)


- 1 Automation system with double pulse input (e.g. PLC)
- 2 Transmitter: observe input values → 🗎 19
- 3 Double pulse output
- 4 Double pulse output (slave), phase-shifted



■ 18 Connection example for double pulse output (passive)

- 1 Automation system with double pulse input (e.g. PLC with a 10 $k\Omega$ pull-up or pull-down resistor)
- 2 Power supply
- 4 Double pulse output
- 5 Double pulse output (slave), phase-shifted


Relay output



■ 19 Connection example for relay output (passive)

- 1 Automation system with relay input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \triangleq 20$


Current input



■ 20 Connection example for 4 to 20 mA current input

- 1 Power supply
- 2 Terminal box
- 3 External measuring device (to read in pressure or temperature, for instance)
- 4 Transmitter

Status input



A002876

21 Connection example for status input

- 1 Automation system with status output (e.g. PLC)
- 2 Power supply
- 3 Transmitter

Terminals

Spring-loaded terminals: Suitable for strands and strands with ferrules. Conductor cross-section 0.2 to 2.5 $\,mm^2$ (24 to 12 AWG).

Cable entries

- Cable gland: M20 \times 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
 - NPT ½"
 - G ½"
 - M20

Pin assignment, device plug

FOUNDATION Fieldbus

	Pin		Assignment	Coding	Plug/socket
2 3	1	+	Signal +	A	Plug
1 4	2	-	Signal –		
	3		Grounding		
	4		Not assigned		


PROFIBUS PA

Pin		Assignment	Coding	Plug/socket
1	+	PROFIBUS PA +	A	Plug
4 2		Grounding		
3	-	PROFIBUS PA -		
4		Not assigned		

Recommended plug:

- Binder, series 713, part no. 99 1430 814 04
- Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

PROFINET



Recommended plug:
Binder, series 825, part no. 99 3729 810 04
Phoenix, part no. 1543223 SACC-M12MSD-4Q

PROFINET with Ethernet-APL

	Pin		Assignment	Coding	Plug/socket
3 4	1	-	APL signal -	А	Socket
2 1	2	+	APL signal +		
\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	3		Cable shield ¹		
	4		Not assigned		
	Metal plug housing		Cable shield		
	¹ If a cable shield is used				

Recommended plug:

■ Binder, series 713, part no. 99 1430 814 04

■ Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

EtherNet/IP


2	Pin		Assignment
	1	+	Tx
1 3	2	+	Rx
	3	-	Tx
	4	-	Rx
4 A0032047	Cod	ling	Plug/socket
	Ι)	Socket

Recommended plug:
Binder, series 763, part no. 99 3729 810 04

■ Phoenix, part no. 1543223 SACC-M12MSD-4Q

Service interface

Order code for "Accessories mounted", option NB: Adapter RJ45 M12 (service interface)



Coding	Plug/socket
D	Socket

Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q

Cable specification

Permitted temperature range

- The installation quidelines that apply in the country of installation must be observed.
- The cables must be suitable for the minimum and maximum temperatures to be expected.

Power supply cable (incl. conductor for the inner ground terminal)

Standard installation cable is sufficient.

Protective grounding cable for the outer ground terminal

Conductor cross-section < 2.1 mm² (14 AWG)

The use of a cable lug enables the connection of larger cross-sections.

The grounding impedance must be less than 2 Ω .

Signal cable

Current output 4 to 20 mA HART

A shielded cable is recommended. Observe grounding concept of the plant.

PROFIBUS PA

Twisted, shielded two-wire cable. Cable type A is recommended.



For further information on planning and installing PROFIBUS networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A	
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz	
Cable capacitance	< 30 pF/m	
Wire cross-section	> 0.34 mm ² (22 AWG)	
Cable type	Twisted pairs	
Loop resistance	≤110 Ω/km	
Signal damping	Max. 9 dB over the entire length of the cable cross-section	
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.	



For further information on planning and installing PROFIBUS networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.



For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization

PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.



For more information on planning and installing PROFINET networks, see: "PROFINET Cabling and Interconnection Technology", Guideline for PROFINET

PROFINET with Ethernet-APL

The reference cable type for APL segments is fieldbus cable type A, MAU type 1 and 3 (specified in IEC 61158-2). This cable meets the requirements for intrinsically safe applications according to IEC TS 60079-47 and can also be used in non-intrinsically safe applications.

Cable type	A		
Cable capacitance	5 to 200 nF/km		
Loop resistance	15 to 150 Ω/km		
Cable inductance	0.4 to 1 mH/km		

Further details are provided in the Ethernet-APL Engineering Guideline (https://www.ethernet-apl.org).

FOUNDATION Fieldbus

Twisted, shielded two-wire cable.



For further information on planning and installing FOUNDATION Fieldbus networks see:

- Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)
- FOUNDATION Fieldbus Guideline
- IEC 61158-2 (MBP)

Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A		
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz		
Cable capacitance	< 30 pF/m		
Wire cross-section	> 0.34 mm ² (22 AWG)		
Cable type	Twisted pairs		
Loop resistance	≤110 Ω/km		
Signal damping	Max. 9 dB over the entire length of the cable cross-section		
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.		

Current output 0/4 to 20 mA

Standard installation cable is sufficient

Pulse /frequency /switch output

Standard installation cable is sufficient

Double pulse output

Standard installation cable is sufficient

Relay output

Standard installation cable is sufficient.

Current input 0/4 to 20 mA

Standard installation cable is sufficient

Status input

Standard installation cable is sufficient

Connecting cable for transmitter - remote display and operating module DKX001 $\,$

Standard cable

A standard cable can be used as the connecting cable.

Standard cable	4 cores (2 pairs); pair-stranded with common shield	
Shielding	'in-plated copper-braid, optical cover ≥ 85 %	
Capacitance: core/shield	Maximum 1000 nF for Zone 1; Class I, Division 1	
L/R	Maximum 24 μH/Ω for Zone 1; Class I, Division 1	
Cable length	Maximum 300 m (1000 ft), see the following table	

Cross-section	Cable length for use in: Non-hazardous area Hazardous area: Zone 2; Class I, Division 2 Hazardous area: Zone 1; Class I, Division 1	
0.34 mm ² (22 AWG)	80 m (270 ft)	
0.50 mm ² (20 AWG)	120 m (400 ft)	
0.75 mm ² (18 AWG)	180 m (600 ft)	
1.00 mm ² (17 AWG)	240 m (800 ft)	
1.50 mm ² (15 AWG)	300 m (1000 ft)	

Optionally available connecting cable

Standard cable	$2\times2\times0.34~\text{mm}^2$ (22 AWG) PVC cable $^{1)}$ with common shield (2 pairs, pair-stranded)
Flame resistance	According to DIN EN 60332-1-2
Oil-resistance	According to DIN EN 60811-2-1
Shielding	Tin-plated copper-braid, optical cover \geq 85 %
Capacitance: core/shield	≤200 pF/m
L/R	<24 μH/Ω
Available cable length	10 m (35 ft)
Operating temperature	When mounted in a fixed position: -50 to $+105$ °C (-58 to $+221$ °F); when cable can move freely: -25 to $+105$ °C (-13 to $+221$ °F)

1) UV radiation can impair the cable outer sheath. Protect the cable from direct sunshine where possible.

Overvoltage protection

Mains voltage fluctuations	→ 🗎 34
Overvoltage category	Overvoltage category II

Short-term, temporary overvoltage	Up to 1200 V between cable and ground, for max. 5 s
Long-term, temporary overvoltage	Up to 500 V between cable and ground

Performance characteristics

Reference operating conditions

- Error limits following DIN EN 29104, in future ISO 20456
- Water, typically: +15 to +45 °C (+59 to +113 °F); 0.5 to 7 bar (73 to 101 psi)
- Data as indicated in the calibration protocol
- Accuracy based on accredited calibration rigs according to ISO 17025
- Reference temperature for conductivity measurement: 25 °C (77 °F)

Maximum measured error

o.r. = of reading


Error limits under reference operating conditions

Volume flow

- ±0.5 % o.r. ± 1 mm/s (0.04 in/s)
- Optional: ±0.2 % o.r. ± 2 mm/s (0.08 in/s)



Fluctuations in the supply voltage do not have any effect within the specified range.



■ 22 Maximum measured error in % o.r.

Temperature

±3 °C (±5.4 °F)

Electrical conductivity


The values apply for:

- Devices with stainless steel process connections
- Measurements at a reference temperature of 25 °C (77 °F). At different temperatures, attention
 must be paid to the temperature coefficient of the medium (typically 2.1 %/K)


Conductivity	Nominal	diameter	Measured error
[µS/cm]	[mm]	[in]	[%] of reading
5 to 20	15 to 150	½ to 6	± 20%
> 20 to 50	15 to 150	½ to 6	± 10%
> 50 to 10 000	2 to 8	½12 to 5/16	± 10%
	15 to 150	½ to 6	■ Standard: ± 10% ■ Optional ¹⁾ : ± 5%

Conductivity	Nominal	diameter	Measured error
[µS/cm]	[mm]	[in]	[%] of reading
> 10 000 to 20 000	2 to 150	½ to 6	± 10%
> 20 000 to 100 000	2 to 150	½ to 6	± 20%

1) Order code for "Calibrated conductivity measurement", option CW



🖪 23 Measured error (standard)



 \blacksquare 24 Measured error (optional: order code for "Calibrated conductivity measurement", option CW)

Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

Accuracy	±5 μA

Pulse/frequency output

o.r. = of reading

Accuracy	Max. ±50 ppm o.r. (over the entire ambient temperature range)
----------	---

Repeatability

o.r. = of reading

Volume flow

Max. ± 0.1 % o.r. \pm 0.5 mm/s (0.02 in/s)

Temperature

±0.5 °C (±0.9 °F)

Electrical conductivity

- Max. ±5 % o.r.
- Max. ±1 % o.r. for DN 15 to 150 in conjunction with process connections made of stainless steel 1.4404 (F316L)

Temperature measurement response time

 T_{90} < 15 s

Influence of ambient temperature

Current output

Temperature coefficient	Max. 1 μA/°C
-------------------------	--------------


Pulse/frequency output

Temperature coefficient	No additional effect. Included in accuracy.
-------------------------	---

Installation


Mounting location

- Do not install the device at the highest point of the pipe.
- Do not install the device upstream from a free pipe outlet in a down pipe.



A0042131

The device should ideally be installed in an ascending pipe.




A00423

Installation upstream from a down pipe

NOTICE

Negative pressure in the measuring pipe can damage the liner!


- ▶ If installing upstream of down pipes whose length $h \ge 5$ m (16.4 ft): install a siphon with a vent valve downstream of the device.
- This arrangement prevents the flow of liquid stopping in the pipe and air entrainment.



- 1 Vent valve
- 2 Pipe siphon
- h Length of down pipe

Installation with partially filled pipes

- Partially filled pipes with a gradient require a drain-type configuration.
- The installation of a cleaning valve is recommended.




A0041088

Installation near pumps

NOTICE

Negative pressure in the measuring pipe can damage the liner!

- ► In order to maintain the system pressure, install the device in the flow direction downstream from the pump.
- ▶ Install pulsation dampers if reciprocating, diaphragm or peristaltic pumps are used.



A0041083

i

- Information on the liner's resistance to partial vacuum


Installation in event of pipe vibrations

A remote version is recommended in the event of strong pipe vibrations.

NOTICE

Pipe vibrations can damage the device!

- ▶ Do not expose the device to strong vibrations.
- ► Support the pipe and fix it in place.
- ► Support the device and fix it in place.
- ▶ Mount the sensor and transmitter separately.



A0041092

i

Information on the measuring system's resistance to vibration and shock $\rightarrow~ \blacksquare~58$

Orientation


The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

Orien	Recommendation	
Vertical orientation	↑ A0015591	✓ ✓
Horizontal orientation	a	1)
Horizontal orientation, transmitter at bottom	A0015590	2) 3) 2 4)
Horizontal orientation, transmitter at side	A0015592	×

- 1) The measuring device should be self-draining for hygiene applications. A vertical orientation is recommended for this. If only a horizontal orientation is possible, an angle of inclination $\alpha \ge 10^\circ$ is recommended.
- 2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.
- 3) To prevent the electronics from overheating in the event of strong heat formation (e.g. CIP or SIP cleaning process), install the device with the transmitter part pointing downwards.
- 4) When the empty pipe detection function is switched on, empty pipe detection only works if the transmitter housing is pointing upwards.


Vertical

Optimum for self-emptying pipe systems and for use in conjunction with empty pipe detection.




Horizontal

- Ideally, the measuring electrode plane should be horizontal. This prevents brief insulation of the measuring electrodes by entrained air bubbles.
- Empty pipe detection only works if the transmitter housing is pointing upwards as otherwise there is no guarantee that the empty pipe detection function will actually respond to a partially filled or empty measuring tube.



A0028998

- EPD electrode for empty pipe detection (available from DN > 15 mm ($\frac{1}{2}$ in))
- 2 Measuring electrodes for signal detection




Inlet and outlet runs


Installation with inlet and outlet runs

To avoid a vacuum and to maintain the specified level of accuracy, install the device upstream from assemblies that produce turbulence (e.g. valves, T-sections) and downstream from pumps.

Maintain straight, unimpeded inlet and outlet runs.



A0028997




A0062132

Adapters

Suitable adapters to DIN EN 545 (double-flange reducers) can be used to install the sensor in larger-diameter pipes. The resultant increase in the rate of flow improves measuring accuracy with very slow-moving fluids.

The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders:


- Calculate the ratio of the diameters d/D.
- From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.
- i
- The nomogram only applies to liquids with a viscosity similar to that of water.
- If the medium has a high viscosity, a larger measuring tube diameter can be considered in order to reduce pressure loss.



A0029002

Special mounting instructions

Weather protection cover



■ 25 Engineering unit mm (in)

Hygienic compatibility



- In the case of measuring devices with the order code for "Housing", option B "Stainless, hygienic", to seal the connection compartment cover, screw it closed finger-tight and tighten it by another 45° (corresponds to 15 Nm).

Environment

Ambient temperature range

Transmitter	Standard: -40 to +60 °C (-40 to +140 °F)
Local display	-20 to $+60$ °C (-4 to $+140$ °F), the readability of the display may be impaired at temperatures outside the temperature range.
Sensor	-40 to +60 °C (-40 to +140 °F)
Liner	Do not exceed or fall below the permitted temperature range of the liner .

If operating outdoors:

- Install the measuring device in a shady location.
- Avoid direct sunlight, particularly in warm climatic regions.
- Avoid direct exposure to weather conditions.



Storage temperature

- Protect the measuring device against direct sunlight during storage in order to avoid unacceptably high surface temperatures.
- Select a storage location where moisture cannot collect in the measuring device as fungus or bacteria infestation can damage the liner.
- If protection caps or protective covers are mounted these should never be removed before installing the measuring device.

Atmosphere

Additional protection against condensation and moisture: the sensor housing is potted with a gel. Order code for "Sensor option", option CF "Harsh environment".

Relative humidity


The device is suitable for use in outdoor and indoor areas with a relative humidity of 4 to 95%.

Operating height According to EN 61010-1 $- \le 2000 \,\mathrm{m} \, (6562 \,\mathrm{ft})$ > 2 000 m (6 562 ft) with additional overvoltage protection (e.g. Endress+Hauser HAW Series) Degree of protection Transmitter ■ IP66/67, Type 4X enclosure, suitable for pollution degree 4 • When the housing is open: IP20, Type 1 enclosure, suitable for pollution degree 2 Display module: IP20, Type 1 enclosure, suitable for pollution degree 2 Optional External WLAN antenna **IP67** Vibration- and shock-Sinusoidal vibration according to IEC 60068-2-6 resistance • 2 to 8.4 Hz, 3.5 mm peak ■ 8.4 to 2000 Hz, 1 g peak Vibration broad-band random, according to IEC 60068-2-64 ■ 10 to 200 Hz, 0.003 g²/Hz ■ 200 to 2000 Hz, 0.001 q²/Hz ■ Total: 1.54 g rms Shock half-sine, according to IEC 60068-2-27 6 ms 30 g Rough handling shocks according to IEC 60068-2-31 Interior cleaning Cleaning in place (CIP) Sterilization in place (SIP) Mechanical load Transmitter housing: • Protect against mechanical effects, such as shock or impact • Do not use as a ladder or climbing aid As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) Electromagnetic compatibility (EMC) Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170 Volume 2, IEC 61784 The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible. Details are provided in the Declaration of Conformity. This unit is not intended for use in residential environments and cannot quarantee adequate protection of the radio reception in such environments. **Process**

58 Endress+Hauser

 $-20 \text{ to } +150 ^{\circ}\text{C} (-4 \text{ to } +302 ^{\circ}\text{F})$

Medium temperature range



T_A Ambient temperature range

 T_F Fluid temperature

The permitted fluid temperature in custody transfer is 0 to +50 $^{\circ}$ C (+32 to +122 $^{\circ}$ F).

Conductivity


 \geq 5 µS/cm for liquids in general.

Pressure-temperature ratings

The following graphics contain material load diagrams (reference curves) for different process connections in relation to the medium temperature.

Process connections with O-ring seal, DN 2 to 25 (1/12 to 1")

Process connection: welding nipple according to DIN EN ISO 1127, ISO 2037; coupling according to ISO 228 / DIN 2999, NPT




■ 26 Process connection material: stainless steel, 1.4404 (F316L)


Endress+Hauser 59

A0028928-EN


Process connection: flange according to EN 1092-1 (DIN 2501), adhesive sleeve



■ 27 Process connection material: stainless steel, 1.4404 (F316L)




■ 28 Process connection material: PVDF




■ 29 Process connection material: PVC-U

Process connection: flange according to ASME B16.5




■ 30 Process connection material: stainless steel, 1.4404 (F316L)




■ 31 Process connection material: PVDF

Process connection: flange according to JIS B2220




32 Process connection material: stainless steel, 1.4404 (F316L)



■ 33 Process connection material: PVDF

Process connections with aseptic gasket seal, DN 2 to 25 (1/12 to 1")


Process connection: welding nipple according to EN 10357, ASME BPE, ISO 2037; Clamp according to ISO 2852, DIN 32676; coupling according to DIN 11851, DIN 11864-1, SMS 1145; flange according to DIN 11864-2



■ 34 Process connection material: stainless steel, 1.4404 (F316L)


Process connections with aseptic gasket seal, DN 40 to 150 (1 $\frac{1}{2}$ to 6")

Process connection: coupling according to SMS 1145




Process connection material: stainless steel, 1.4404 (F316L)

Process connection: welding nipple according to EN 10357; coupling according to DIN 11851




■ 36 Process connection material: stainless steel, 1.4404 (F316L)

Process connection: welding nipple according to ASME BPE




A0028942-EN

Process connection: welding nipple according to ISO 2037




37 Process connection material: stainless steel, 1.4404 (F316L)

Process connection: clamp according to ISO 2852, DIN 32676




■ 38 Process connection material: stainless steel, 1.4404 (F316L)

Process connection: coupling according to DIN 11864-1, ISO 2853



■ 39 Process connection material: stainless steel, 1.4404 (F316L)

Process connection: flange according to DIN 11864-2



A0028945-E1

■ 40 Process connection material: stainless steel, 1.4404 (F316L)

Pressure tightness

Liner: PFA

Nominal diameter			Limit values for absolute pressure in [mbar] ([psi]) for medium temperatures:							
	[mm] [in]		+25 °C (+77 °F)	+80 °C (+176 °F)	+100 °C (+212 °F)					
	2 to 150	½12 to 6	0 (0)	0 (0)	0 (0)	0 (0)	0 (0)			

Flow limit

The diameter of the pipe and the flow rate determine the nominal diameter of the sensor. The optimum velocity of flow is between 2 to 3 m/s (6.56 to 9.84 ft/s). Also match the velocity of flow (v) to the physical properties of the medium:

- v < 2 m/s (6.56 ft/s): for low conductivity values
- v > 2 m/s (6.56 ft/s): for media producing buildup (e.g. milk with a high fat content)
- A necessary increase in the flow velocity can be achieved by reducing the sensor nominal diameter.
- For an overview of the full scale values for the measuring range, see the "Measuring range" section

Pressure loss

- ullet No pressure loss occurs as of nominal diameter DN 8 (5/16") if the sensor is installed in a pipe with the same nominal diameter.
- Pressure losses for configurations incorporating adapters according to DIN EN 545 \Rightarrow \triangleq 56


System pressure

Installation near pumps $\rightarrow \triangleq 53$

Vibrations

Installation in event of pipe vibrations $\rightarrow \implies 53$

Magnetism and static electricity




A0042152

41 Avoid magnetic fields

Mechanical construction

Dimensions in SI units

Compact version



Order code for "Housing", option A "Aluminum, coated"

DN	A 1)	B 1)	С	D	Е	F	G 2)	Н	I 2)	K	L 3)	M
[mm]	[mm]	[mm]										
2	169	68	101	55	240	295	200	59	141	2.25	86	43
4	169	68	101	55	240	295	200	59	141	4.5	86	43
8	169	68	101	55	240	295	200	59	141	9	86	43
15	169	68	101	55	240	295	200	59	141	16	86	43
25	169	68	101	55	240	295	200	59	141	22.6	86	56
40	169	68	101	54	239	293	200	59	141	34.8	140	107
50	169	68	101	60	246	306	200	59	141	47.5	140	120
65	169	68	101	68	254	322	200	59	141	60.2	140	135
80	169	68	101	74	260	334	200	59	141	72.9	140	148
100	169	68	101	87	273	360	200	59	141	97.4	140	174
125	169	68	101	103	289	392	200	59	141	120.0	200	206
150	169	68	101	117	303	420	200	59	141	146.9	200	234

- Depending on the cable gland used: values up to \pm 30 mm For version without local display: values \pm 30 mm
- 1) 2)
- 3) Total installed length depends on process connections. → 🖺 69

Order code for "Housing", option A "Aluminum, coated"; Ex d

DN	A 1)	B 1)	С	D	Е	F	G 2)	Н	I 2)	K	L 3)	М
[mm]												
2	188	85	103	55	269	324	217	58	159	2.25	86	43
4	188	85	103	55	269	324	217	58	159	4.5	86	43
8	188	85	103	55	269	324	217	58	159	9	86	43
15	188	85	103	55	269	324	217	58	159	16	86	43
25	188	85	103	55	269	324	217	58	159	22.6	86	56
40	188	85	103	54	270	324	217	58	159	34.8	140	107

66

DN	A 1)	B 1)	С	D	Е	F	G ²⁾	Н	I 2)	K	L 3)	M
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]							
50	188	85	103	60	276	336	217	58	159	47.5	140	120
65	188	85	103	67	284	351	217	58	159	60.2	140	135
80	188	85	103	74	290	364	217	58	159	72.9	140	148
100	188	85	103	87	303	390	217	58	159	97.4	140	174
125	188	85	103	103	319	422	217	58	159	120.0	200	206
150	188	85	103	117	333	450	217	58	159	146.9	200	234

- Depending on the cable gland used: values up to + 30 mm 1)
- 2) 3) For version without local display: values – 40 mm


 Total installed length depends on process connections. → 🖺 69

Order code for "Housing", option B "Stainless, hygienic"

DN	A 1)	B 1)	С	D	Е	F	G ²⁾	Н	I 2)	K	L ³⁾	M
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]							
2	183	73	110	55	254	309	207	65	142	2.25	86	43
4	183	73	110	55	254	309	207	65	142	4.5	86	43
8	183	73	110	55	254	309	207	65	142	9	86	43
15	183	73	110	55	254	309	207	65	142	16	86	43
25	183	73	110	55	254	309	207	65	142	22.6	86	56
40	183	73	110	54	255	309	207	65	142	34.8	140	107
50	183	73	110	60	261	321	207	65	142	47.5	140	120
65	183	73	110	67	269	336	207	65	142	60.2	140	135
80	183	73	110	74	275	349	207	65	142	72.9	140	148
100	183	73	110	87	288	375	207	65	142	97.4	140	174
125	183	73	110	103	304	407	207	65	142	120.0	200	206
150	183	73	110	117	318	435	207	65	142	146.9	200	234


- Depending on the cable gland used: values up to + 30 mm 1)
- 2) For version without local display: values – 30 mm
- Total installed length depends on process connections. → 🖺 69

Sensor flange connection



■ 42 Front view without process connections

DN	Α	В	С	D	Е	F	G	Н	К	L	M
[mm]											
2	62	41.6	34	9	24	42	43	8.5	6	4	M6
4	62	41.6	34	9	24	42	43	8.5	6	4	M6
8	62	41.6	34	9	24	42	43	8.5	6	4	M6
15	62	41.6	34	16	24	42	43	8.5	6	4	M6
25	72	50.2	44	26	29	55	56	8.5	6	4	M6



 \blacksquare 43 Front view without process connections

DN	Α	В	С	D	Е	F	G	Н	К	L
									90° ±0.5°	60° ±0.5°
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	Tappe	d holes
40	99.7	85.8	71.0	48.3	34.8	M8	12	17	4	-
50	112.7	98.8	83.5	60.3	47.5	M8	12	17	4	-
65	127.7	114.8	100.0	76.1	60.2	M8	12	17	-	6
80	140.7	133.5	114.0	88.9	72.9	M8	12	17	-	6


Endress+Hauser

A001765

DN	Α	В	С	D	E	F	G	Н	K	L
									90° ±0.5°	60° ±0.5°
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	Tappe	d holes
100	166.7	159.5	141.0	114.3	97.4	M8	12	17	-	6
125	198.7	191.5	171.0	139.7	120.0	M10	15	20	-	6
150	226.7	219.5	200.0	168.3	146.9	M10	15	20	-	6

Flange connections

Female with aseptic gasket seal



■ 44 Detail X: Asymmetrical process connection; the part shown in blue is provided by the supplier.

1.4404 (316L), suitable for pipe according to EN 10357 series A, female Order code for "Process connection", option DES/DQS Suitable for pipe according to EN 10357 series DN В С D Ε [mm] [mm] [mm] [mm] [mm] [mm] [mm] [mm] 2 to 8 $^{1)}$ 13 × 1.5 (DN 10) 183 54 37 $4 \times Ø9$ 10 10 15 19 × 1.5 (DN 15) 59 42 $4 \times Ø9$ 10 16 183 29 × 1.5 (DN 25) 25 70 53 4 × Ø9 10 26 183


Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (E) when cleaning with pigs.

1) With DN 10 flanges as standard

Flange DIN 11864-2, aseptic female, Form A

Flange with notch with aseptic gasket seal




■ 45 Detail X: Asymmetrical process connection; the part shown in blue is provided by the supplier.

Flange DIN 11864-2, aseptic flange with notch, Form A 1.4404 (316L), suitable for pipe according to EN 10357 series A, flange with notch Order code for "Process connection", option DES/DRS DN Suitable for pipe according to EN 10357 series В С D Е Α L [mm] [mm] [mm] [mm] [mm] [mm] [mm] [mm] 40 41 × 1.5 82 65 $4 \times Ø9$ 10 38 246 50 53 × 1.5 94 77 4 × Ø9 10 50 246 65 70 × 2 113 95 8 × Ø9 66 246 80 85 × 2 133 112 8 × Ø11 10 81 270 100 159 137 100 278 104×2 8 × Ø11 10 125 129 × 2 183 161 8 × Ø11 10 125 362 150 154 × 2 213 188 8 × Ø14 150 362

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (E) when cleaning with pigs.

Flanges with O-ring seal



70 Endress+Hauser

A001562

Flange according to EN 1092-1 (DIN 2501), Form B: PN 40 1.4404 (316L) Order code for "Process connection", option D5S											
DN A B C D E L [mm] [mm] [mm] [mm] [mm]											
2 to 8 ¹⁾	95	65	4 × Ø14	16	17.3	198.4					
15	95	65	4 × Ø14	16	17.3	198.4					
25 115 85 4 × Ø14 18 28.5 198.4											
Surface roughness: $Ra_{max} = 1.6 \mu m$											


DN 2 to 8 with DN 15 flanges as standard

Flange according to ASME B16.5: Class 150 1.4404 (316L) Order code for "Process connection", option A1S										
DN A B C D E L [mm] [mm] [mm] [mm] [mm]										
2 to 8 ¹⁾	90	60.3	4 × Ø15.7	11.2	15.7	218				
15	90	60.3	4 × Ø15.7	11.2	15.7	218				
25 110 79.4 4 × Ø15.7 14.2 26.7 230										
Surface roughness: $Ra_{max} = 1.6 \mu m$										

1) DN 2 to 8 with DN 15 flanges as standard $\,$

Flange according to JIS B2220: 20K 1.4404 (316L) Order code for "Process connection", option N4S											
DN A B C D E L											
2 to 8 ¹⁾	95	70	4 × Ø15	14	15	220					
15	95	70	4 × Ø15	14	15	220					
25 125 90 4ר19 16 25 220											
Surface roughness: $Ra_{max} = 1.6 \mu m$											

DN 2 to 8 with DN 15 flanges as standard



Lap joint flange according to EN 1092-1 (DIN 2501): PN 16 PVDF

Order code for "Process connection", option D3P

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]
2 to 8 ¹⁾	95	65	4 x Ø14	14.5	45	17.3	200
15	95	65	4 x Ø14	14.5	45	17.3	200
25	115	85	4 x Ø14	16.5	68	28.5	200

Surface roughness: $Ra_{max} = 1.6 \mu m$

The required grounding rings can be ordered as accessories (order code: DK5HR-****).

1) DN 2 to 8 with DN 15 flanges as standard

Lap joint flange with grounding electrode according to EN 1092-1 (DIN 2501): PN 16 PVDF $_$

Order code for "Process connection", option D4P

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]
2 to 8 ¹⁾	95	65	4 x Ø14	14.5	45	17.3	200
15	95	65	4 x Ø14	14.5	45	17.3	200
25	115	85	4 x Ø14	16.5	68	28.5	200

Surface roughness: $Ra_{max} = 1.6 \mu m$ Grounding rings are not necessary.

1) DN 2 to 8 with DN 15 flanges as standard

Lap joint flange according to ASME B16.5: Class 150

Order code for "Process connection", option A1P

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]
2 to 8 ¹⁾	90	60.3	4 × Ø 15.7	15	35.1	15.7	200
15	90	60.3	4 × Ø 15.7	15	35.1	15.7	200
25	110	79.4	4 × Ø 15.7	16	50.8	26.7	200

Surface roughness: $Ra_{max} = 1.6 \mu m$

The required grounding rings can be ordered as accessories (order code: DK5HR-****).

1) DN 2 to 8 with DN 15 flanges as standard

Lap joint flange with grounding electrode according to ASME B16.5: Class 150 PVDF

Order code for "Process connection", option A4P

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]
2 to 8 ¹⁾	90	60.3	4 × Ø 15.7	15	35.1	15.7	200
15	90	60.3	4 × Ø 15.7	15	35.1	15.7	200
25	110	79.4	4 × Ø 15.7	16	50.8	26.7	200

Surface roughness: $Ra_{max} = 1.6 \ \mu m$ Grounding rings are not necessary.

1) DN 2 to 8 with DN 15 flanges as standard

72

Lap joint flange according to JIS B2220: 10K PVDF

Order code for "Process connection", option N3P

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]
2 to 8 ¹⁾	95	70	4 × Ø 15.7	15	35.1	15	200
15	95	70	4 × Ø 15.7	15	35.1	15	200
25	125	90	4 × Ø 15.7	16	50.8	19	200

Surface roughness: Ra_{max} = 1.6 μm The required grounding rings can be ordered as accessories (order code: DK5HR-****).

1) DN 2 to 8 with DN 15 flanges as standard


Lap joint flange with grounding electrode according to JIS B2220: 10K PVDF Order code for "Process connection", option N4P							
DN A B C D E F L [mm] [mm] [mm] [mm] [mm] [mm]							
2 to 8 1)	95	70	4 × Ø 15.7	15	35.1	15	200
15	95	70	4 × Ø 15.7	15	35.1	15	200
25	125	90	4 × Ø 15.7	16	50.8	19	200
Curfo co nough	Surface voughnoon Do = 1.6 um						

Surface roughness: Ra_{max} = 1.6 μm Grounding rings are not necessary.

1) DN 2 to 8 with DN 15 flanges as standard

Welding nipple

Welding nipple with aseptic gasket seal



Welding nipple according to EN 10357
1.4404 (316L), suitable for pipe EN 10357 series A
Order code for "Process connection", option DAS

	,,							
DN [mm]	Suitable for pipe EN 10357 series A [mm]	A [mm]	B [mm]	L [mm]				
2 to 8	13 × 1.5	13	10	132.6				
15	19 × 1.5	19	16	132.6				
25	29 × 1.5	29	26	132.6				
40	41 × 1.5	41	38	220				
50	53 × 1.5	53	50	220				
65	70 × 2	70	66	220				
80	85 × 2	85	81	220				

Welding nipple according to EN 10357

1.4404 (316L), suitable for pipe EN 10357 series A

Order code for "Process connection", option DAS

DN [mm]	Suitable for pipe EN 10357 series A [mm]	A [mm]	B [mm]	L [mm]
100	104 × 2	104	100	220
125	129 × 2	129	125	300
150	154 × 2	154	150	300

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Welding nipple according to ISO 2037 1.4404 (316L), suitable for pipe ISO 2037

Order code for "Process connection", option IAS

* *			
Suitable for pipe ISO 2037 [mm]	A [mm]	B [mm]	L [mm]
12.7 × 1.65	12	10	118.2
19.05 × 1.65	18	16	118.2
25.4 × 1.60	25	22.6	118.2
38 × 1.2	38	35.6	220
51 × 1.2	51	48.6	220
63.5 × 1.6	63.5	60.3	220
76.1 × 1.6	76.1	72.9	220
101.6 × 2	101.6	97.6	220
139.7 × 2	139.7	135.7	380
168.3 × 2.6	168.3	163.1	380
	[mm] 12.7×1.65 19.05×1.65 25.4×1.60 38×1.2 51×1.2 63.5×1.6 76.1×1.6 101.6×2 139.7×2	[mm][mm] 12.7×1.65 12 19.05×1.65 18 25.4×1.60 25 38×1.2 38 51×1.2 51 63.5×1.6 63.5 76.1×1.6 76.1 101.6×2 101.6 139.7×2 139.7	[mm][mm][mm] 12.7×1.65 1210 19.05×1.65 1816 25.4×1.60 2522.6 38×1.2 3835.6 51×1.2 5148.6 63.5×1.6 63.560.3 76.1×1.6 76.172.9 101.6×2 101.697.6 139.7×2 139.7135.7

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Welding nipple according to ASME BPE

1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series $\mbox{\it C}$


Order code for "Process connection", option AAS

DN [mm]	Suitable for pipe according to ASME BPE [mm]	A [mm]	B [mm]	L [mm]
2 to 8	12.7 × 1.65	12.7	9	118.2
15	19.1 × 1.65	19.1	16	118.2
25	25.4 × 1.65	25.4	22.6	118.2
40	38.1 × 1.65	38.1	34.8	220
50	50.8 × 1.65	50.8	47.5	220
65	63.5 × 1.65	63.5	60.2	220
80	76.2 × 1.65	76.2	72.9	220
100	101.6 × 1.65	101.6	97.4	220
150	152.4 × 2.77	152.4	146.9	300

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Welding nipple with O-ring seal



A002751


Welding nipple according to ISO 1127 1.4404 (316L), suitable for pipe according to ISO 1127 series 1 Order code for "Process connection", option A2S							
DN [mm]	Suitable for pipe according to ISO 1127 series 1 [mm]	A [mm]	B [mm]	L [mm]			
2 to 8	13.5 × 2.30	13.5	9	126.6			
15	21.3 × 2.65	21.3	16	126.6			
25	33.7 × 3.25	33.7	27.2	126.6			
Surface ro	Surface roughness: Ra _{max} = 1.6 µm						

1.4404	Welding nipple according to ISO 1127 1.4404 (316L), suitable for pipe according to ISO 1127 series 1 and DIN 11866 series B Order code for "Process connection", option D1S						
DN [mm]	Suitable for pipe according to ISO 1127 series 1 and DIN 11866 series B [mm]	A [mm]	B [mm]	L [mm]			
2 to 8	13.5 × 1.6	13.5	10.3	126.6			
15	21.3 × 1.6	21.3	18.1	126.6			
25	33.7 × 2.0	33.7	29.7	126.6			
Surface	Surface roughness: Ra = 1.6 µm						

Welding nipple according to ISO 2037 1.4404 (316L), suitable for pipe ISO 203 Order code for "Process connection", option I1S					
DN [mm]	Suitable for pipe ISO 2037 [mm]	A [mm]	B [mm]	L [mm]	
2 to 8	13.5 × 2.3	13.5	9	126.6	
15	21.3 × 2.65	21.3	16	126.6	
25	33.7 × 3.25	33.7	27.2	126.6	
Surface roughness: Ra _{max} = 1.6 μm					

Clamp connections

Clamp connections with aseptic gasket seal



Clamp according to DIN 32676 1.4404 (316L)_

Oraer coae for "Proc	Order code for Process connection, option DBS								
DN [mm]	Suitable for pipe [mm]	A [mm]	B [mm]	L [mm]					
2 to 8	14 × 2 (DN 10)	34	10	168					
15	20 × 2 (DN 15)	34	16	168					
25	30 × 2 (DN 25)	50.5	26	175					
40	41 × 1.5	50.5	38	220					
50	53 × 1.5	64	50	220					
65	70 × 2	91	66	220					
80	85 × 2	106	81	220					
100	104 × 2	119	100	220					
125	129 × 2	155	125	300					
150	154 × 2	183	150	300					

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished
Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Tri-Clamp 1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C Order code for "Process connection", option FAS					
DN [mm]	Suitable for pipe according to ASME BPE [mm]	A [mm]	B [mm]	L [mm]	
2 to 8	12.7 × 1.65	25	9.4	143	
15	19.1 × 1.65	25	15.8	143	
25	25.4 × 1.65	50.4	22.1	143	
40	38.1 × 1.65	50.4	34.8	220	
50	50.8 × 1.65	63.9	47.5	220	
65	63.5 × 1.65	77.4	60.2	220	
80	76.2 × 1.65	90.9	72.9	220	
100	101.6 × 2.11	118.9	97.4	220	

Tri-Clamp

1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C

Order code for "Process connection", option FAS

DN	Suitable for pipe according to ASME BPE [mm]	A	B	L
[mm]		[mm]	[mm]	[mm]
150	152.4 × 2.77	166.9	146.9	300

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Clamp according to ISO 2852, Fig. 2 1.4404 (316L)

Order code for "Process connection", option IBS


,	' L			
DN [mm]	Suitable for pipe ISO 2037 [mm]	A [mm]	B [mm]	L [mm]
25	24.5 × 1.65	50.5	22.6	174.6
40	38 × 1.6	50.5	35.6	220
50	51 × 1.6	64	48.6	220
65	63.5 × 1.6	77.5	60.3	220
80	76.1 × 1.6	91	72.9	220
100	101.6 × 2	119	97.6	220
125	139.7 × 2	155	135.7	300
150	168.3 × 2.6	183	163.1	300

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Couplings

Thread with aseptic gasket seal



A0027509

Coupling DIN 11851, thread

1.4404 (316L), suitable for pipe EN 10357 series B

Order code for "Process connection", option DCS

Oraci coac joi	oraci code for Process connection, option Des						
DN [mm]	Suitable for pipe EN 10357 series B [mm]	A [mm]	B [mm]	L [mm]			
2 to 8	12 × 1 (DN 10)	Rd 28 × 1/8	10	174			
15	18 × 1.5	Rd 34 × ½	16	174			
25	28 × 1 or 28×1.5	Rd 52 × ½	26	190			

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling DIN 11851, thread

1.4404 (316L), suitable for pipe EN 10357 series A

Order code for "Process connection", option DCS

DN [mm]	Suitable for pipe EN 10357 series A [mm]	A [mm]	B [mm]	L [mm]
40	41 × 1.5	Rd 65 × 1/ ₆	38	260
50	53 × 1.5	Rd 78 × 1/ ₆	50	260
65	70 × 2	Rd 95 × 1/ ₆	66	270
80	85 × 2	Rd 110 × 1/4	81	280
100	104 × 2	Rd 130 × 1/4	100	290
125	129 × 2	Rd 160 × 1/4	125	380
150	154 × 2	Rd 160 × 1/4	150	390

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling DIN 11864-1, aseptic thread, Form A 1.4404 (316L), suitable for pipe EN 10357 series A

Order code for "Process connection", option **DDS**

- · · · · · · · · · · · · · · · · · · ·	,					
DN [mm]	Suitable for pipe EN 10357 series A [mm]	A [mm/in]	B [mm]	L [mm]		
2 to 8	13 × 1.5 (DN 10)	Rd 28 × 1/8	10	170		
15	19 × 1.5	Rd 34 × 1/8	16	170		
25	29 × 1.5	Rd 52 × 1/ ₆	26	184		
40	41 × 1.5	Rd 65 × 1/ ₆	38	256		
50	53 × 1.5	Rd 78 × 1/6	50	256		
65	70 × 2	Rd 95 × 1/6	66	266		
80	85 × 2	Rd 110 × 1/4	81	276		
100	104 × 2	Rd 130 × 1/4	100	286		

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling ISO 2853, thread

1.4404 (316L)

Order code for "Process connection", option ICS

DN [mm]	Suitable for pipe ISO 2037 [mm]	DN Clamp ISO 2853 [mm]	A [mm/in]	B [mm]	L [mm]
40	38 × 1.6	38	Tr 50.5 × 3.175	35.6	256
50	51 × 1.6	51	Tr 64 × 3.175	48.6	256
65	63.5 × 1.6	63.5	Tr 77.5 × 3.175	60.3	266
80	76.1 × 1.6	76.1	Tr 91 × 3.175	72.9	276
100	101.6 × 2	101.6	Tr 118 × 3.175	97.6	286

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling SMS 1145, thread 1.4404 (316L)


Order code for "Process connection", option SAS

DN [mm]	Suitable for pipe [mm]	DN SMS 1145 [mm]	A [mm/in]	B [mm]	L [mm]
25	1	25	Rd 40 × 1/ ₆	22.6	147.6
40	38.1 × 1.65	38	Rd 60 × 1/ ₆	34.8	256
50	50.8 × 1.65	51	Rd 70 × 1/ ₆	47.5	256
65	63.5 × 1.65	63.5	Rd 85 × 1/ ₆	60.2	266
80	76.2 × 1.65	76	Rd 98 × 1/ ₆	72.6	276
100	101.6 × 1.65	101.6	Rd 132 × ½	97.4	286

Surface roughness: $Ra_{max} = 0.76 \ \mu m$, optional order code for "Service", option HJ: $Ra_{max} = 0.38 \ \mu m$

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Thread with O-ring seal



A0027509

DN	A					
Order code for "Proc	Order code for "Process connection", option I2S					
1.4404 (316L)						
External thread according to ISO 228/DIN 2999						


DN [mm]	Suitable for internal thread ISO 228/DIN 2999 [in]	A [mm/in]	B [mm]	L [mm]
2 to 8	R 3/8	R 10.1 × ³ / ₈	10	166
15	R ½	R 13.2 × ½	16	166
25	R 1	R 16.5 × 1	25	170

Surface roughness: $Ra_{max} = 1.6 \mu m$

Internal thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I3S							
DN Suitable for external A B [mm] thread ISO 228/DIN 2999 [mm/in] [mm] [[in]							
2 to 8	Rp ³ / ₈	Rp 13 × 3/ ₈	9	176			
15	Rp ⅓	Rp 14 × ½	16	176			
25 Rp 1 Rp 17 × 1 27.2 188							
Surface roughness: Ra _{max} = 1.6 μm							

Hose adapter

Hose adapter with O-ring seal




AUU2/511

Hose adapter 1.4404 (316L) Order code for "Process connection", options O1S, O2S, O3S					
DN [mm]	Suitable for internal diameter [mm]	A [mm]	L [mm]		
2 to 8	13	10	184		
15	16	12.6	184		
25	19	16	184		
Surface roughness: Ra _{max} = 1.6 µm					

Adhesive sleeves


Adhesive sleeves with O-ring seal



Adhesive sleeve PVC Order code for "Process connection", option O2V							
DN [mm]	Suitable for pipe [mm] / [in]	A [mm]	B [mm]	C [mm]	D [mm]	L [mm]	
2 to 8	20 × 2	62	38.5	18	20.2	163	
15	(DIN 8062)		28.0			142	
Surface roughness: $Ra_{max} = 1.6 \mu m$ The required grounding rings can be ordered as accessories (order code: DK5HR-***).							

Mounting kits

Wall mounting kit




A0005537

A	В	С	Ø D	Е	F
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
137	110	120	7	125	88


Accessories

Weather protection cover



■ 46 Engineering unit mm (in)

Remote display and operating module DKX001




■ 47 Engineering unit mm (in)

External WLAN antenna

The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



■ 48 Engineering unit mm (in)


External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/reception conditions at the transmitter mounting location are poor.




■ 49 Engineering unit mm (in)

Spacer



Order code: DK5HB-**** L DN D1 D2 di [mm] [mm] [mm] [mm] [mm] 80 72.9 140.7 141 30 30 100 97.4 166.7 162

 ${\it Clamp\ connections\ with\ aseptic\ gasket\ seal\ available\ for\ order}$



Endress+Hauser 83

A001729

Tri-Clamp


1.4404 (316L), suitable for pipe according to ASME BPE and BS 4825, reduction from pipe OD 1" (Tri-Clamp connection) to device DN 15 Order code: DKH**-HF**

DN [mm]	Suitable for pipe according to ASME BPE and BS 4825 (reduction) [mm]	A [mm]	B [mm]	L [mm]
15	Pipe OD 1"	50.4	22.1	143

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Design", option CB: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.


Couplings with O-ring seal available for order



1.4404 (31	External thread 1.4404 (316L) Order code: DKH**-GD**												
DN [mm]	Suitable for internal thread NPT [in]	A [mm/in]	B [mm]	L [mm]									
2 to 8	NPT 3/8	R 15.5 × 3/8	10	186									
15	NPT ½	R 20 × ½	16	186									
25	NPT 1	R 25 × 1	25	196									
Surface roughness: Ra _{max} = 1.6 μm													

1.4404 (31	Internal thread 1.4404 (316L) Order code: DKH**-GC**												
DN [mm]	Suitable for external thread NPT [in]	A [mm/in]	B [mm]	L [mm]									
2 to 8	NPT 3/8	R 13 × 3/8	8.9	176									
15	NPT ½	R 14 × ½	16	176									
25	NPT 1	R 17 × 1	27.2	188									
Surface rou	Surface roughness: $Ra_{max} = 1.6 \mu m$												

Grounding rings




For lap joint flange made of PVDF and PVC adhesive sleeve 1.4435 (316L), Alloy C22, tantalum Order code: DK5HR-****

DN	di	В	С	D	E	F	G	Н	J
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
2 to 8	9	22	17.6	33.9	0.5	3.5	1.9	3.4	4.5
15	16	29	24.6	33.9	0.5	3.5	1.9	3.4	4.5
25	26	39	34.6	43.9	0.5	3.5	1.9	3.4	4.5

Dimensions in US units

Compact version



Order code for "Housing", option A "Aluminum, coated"

DN	A 1)	B 1)	С	D	Е	F	G ²⁾	Н	I 2)	K	L 3)	M
[in]	[in]	[in]	[in]	[in]	[in]							
1/12	6.65	2.68	3.98	2.17	9.45	11.6	7.87	2.32	5.55	0.09	3.39	1.69
1/8	6.65	2.68	3.98	2.17	9.45	11.6	7.87	2.32	5.55	0.18	3.39	1.69
3/8	6.65	2.68	3.98	2.17	9.45	11.6	7.87	2.32	5.55	0.35	3.39	1.69
1/2	6.65	2.68	3.98	2.17	9.45	11.6	7.87	2.32	5.55	0.63	3.39	1.69
1	6.65	2.68	3.98	2.17	9.45	11.6	7.87	2.32	5.55	0.89	3.39	2.20

DN	A 1)	B 1)	С	D	Е	F	G 2)	Н	I 2)	K	L 3)	M
[in]												
1 ½	6.65	2.68	3.98	2.13	9.41	11.5	7.87	2.32	5.55	1.37	5.51	4.21
2	6.65	2.68	3.98	2.36	9.69	12.1	7.87	2.32	5.55	1.87	5.51	4.72
3	6.65	2.68	3.98	2.91	10.2	13.2	7.87	2.32	5.55	2.87	5.51	5.83
4	6.65	2.68	3.98	3.43	10.8	14.2	7.87	2.32	5.55	3.83	5.51	6.85
6	6.65	2.68	3.98	4.61	11.9	16.5	7.87	2.32	5.55	5.78	7.87	9.21

- 1) Depending on the cable gland used: values up to + 1.18 in
- 2) 3) For version without local display: values – 1.18 in
- Total installed length depends on process connections. \rightarrow $\stackrel{\frown}{\blacksquare}$ 88

Order code for "Housing", option A "Aluminum, coated"; Ex d

DN	A 1)	B 1)	С	D	Е	F	G 2)	Н	I 2)	K	L 3)	M
[in]												
1/12	7.40	3.35	4.06	2.17	10.6	12.8	8.54	2.28	6.26	0.09	3.39	1.69
1/8	7.40	3.35	4.06	2.17	10.6	12.8	8.54	2.28	6.26	0.18	3.39	1.69
3/8	7.40	3.35	4.06	2.17	10.6	12.8	8.54	2.28	6.26	0.35	3.39	1.69
1/2	7.40	3.35	4.06	2.17	10.6	12.8	8.54	2.28	6.26	0.63	3.39	1.69
1	7.40	3.35	4.06	2.17	10.6	12.8	8.54	2.28	6.26	0.89	3.39	2.20
1 ½	7.40	3.35	4.06	2.13	10.6	12.8	8.54	2.28	6.26	1.37	5.51	4.21
2	7.40	3.35	4.06	2.36	10.9	13.2	8.54	2.28	6.26	1.87	5.51	4.72
3	7.40	3.35	4.06	2.91	11.4	14.3	8.54	2.28	6.26	2.87	5.51	5.83
4	7.40	3.35	4.06	3.43	11.9	15.4	8.54	2.28	6.26	3.83	5.51	6.85
6	7.40	3.35	4.06	4.61	13.1	17.7	8.54	2.28	6.26	5.78	7.87	9.21


- Depending on the cable gland used: values up to \pm 1.18 in 1)
- 2) 3) For version without local display: values – 1.57 in
- Total installed length depends on process connections. → 🖺 88

Order code for "Housing", option B "Stainless, hygienic"

DN	A 1)	B 1)	С	D	Е	F	G ²⁾	Н	I 2)	К	L 3)	M
[in]	[in]	[in]	[in]	[in]	[in]							
1/12	7.20	2.87	4.33	2.17	10.0	12.2	8.15	2.56	5.59	0.09	3.39	1.69
1/8	7.20	2.87	4.33	2.17	10.0	12.2	8.15	2.56	5.59	0.18	3.39	1.69
3/8	7.20	2.87	4.33	2.17	10.0	12.2	8.15	2.56	5.59	0.35	3.39	1.69
1/2	7.20	2.87	4.33	2.17	10.0	12.2	8.15	2.56	5.59	0.63	3.39	1.69
1	7.20	2.87	4.33	2.17	10.0	12.2	8.15	2.56	5.59	0.89	3.39	2.20
1 ½	7.20	2.87	4.33	2.13	10.0	12.2	8.15	2.56	5.59	1.37	5.51	4.21
2	7.20	2.87	4.33	2.63	10.3	12.6	8.15	2.56	5.59	1.87	5.51	4.72
3	7.20	2.87	4.33	2.91	10.8	13.7	8.15	2.56	5.59	2.87	5.51	5.83
4	7.20	2.87	4.33	3.43	11.3	14.8	8.15	2.56	5.59	3.83	5.51	6.85
6	7.20	2.87	4.33	4.61	12.5	17.1	8.15	2.56	5.59	5.78	7.87	9.21


- 1) Depending on the cable gland used: values up to \pm 1.18 in
- 2) For version without local display: values – 1.18 in
- 3) Total installed length depends on process connections. → 🖺 88

Sensor flange connection



■ 50 Front view without process connections

DN	Α	В	С	D	Е	F	G	Н	К	L	М
[in]	[mm]										
1/12	2.44	1.64	1.34	0.35	0.94	1.65	1.69	0.33	0.24	0.16	M6
5/32	2.44	1.64	1.34	0.35	0.94	1.65	1.69	0.33	0.24	0.16	M6
5/16	2.44	1.64	1.34	0.35	0.94	1.65	1.69	0.33	0.24	0.16	M6
1/2	2.44	1.64	1.34	0.63	0.94	1.65	1.69	0.33	0.24	0.16	M6
1	2.83	1.98	1.73	0.89	1.14	2.17	2.20	0.33	0.24	0.16	M6




 \blacksquare 51 Front view without process connections

DN	Α	В	С	D	Е	F	G	Н	К	L
									90° ±0.5°	60° ±0.5°
[in]	[in]	[in]	[in]	[in]	[in]	[mm]	[in]	[in]	Тарре	d holes
1 1/2	3.93	3.38	2.80	1.90	1.37	M8	0.47	0.67	4	-
2	4.44	3.89	3.29	2.37	1.87	M8	0.47	0.67	4	-
3	5.54	5.26	4.49	3.50	2.87	M8	0.47	0.67	-	6
4	6.56	6.28	5.55	4.50	3.83	M8	0.47	0.67	-	6

DN	A	В	С	D	Е	F	G	Н	К	L
									90° ±0.5°	60° ±0.5°
[in]	[in]	[in]	[in]	[in]	[in]	[mm]	[in]	[in]	Тарре	d holes
5	7.82	7.54	6.73	5.50	4.72	M10	0.59	0.79	-	6
6	8.93	8.64	7.87	6.63	5.78	M10	0.59	0.79	-	6


Flange connections

Flanges with O-ring seal



Flange according to ASME B16.5: Class 150 1.4404 (316L) Order code for "Process connection", option A1S DN В С D Ε [in] [in] [in] [in] [in] [in] [in] $^{1}\!/_{12}$ to $^{3}\!/_{8}$ $^{1)}$ 3.50 2.38 $4 \times \emptyset 0.62$ 0.44 0.62 8.59 3.50 1/2 2.38 $4 \times \emptyset 0.62$ 0.44 0.63 8.59 4.25 3.12 4 × Ø0.62 0.56 1.05 9.05 Surface roughness: $Ra_{max} = 63 \mu in$

1) DN $\frac{1}{12}$ to $\frac{3}{8}$ with DN $\frac{1}{2}$ " flanges as standard



PVDF Order code for "Process connection", option A1P							
DN A B C D E F L [in] [in] [in] [in] [in] [in] [in]							
½12 to 3/8 1)	3.74	2.36	4 × Ø 0.62	0.59	1.38	0.63	7.87
1/2	3 74	2.36	4 × Ø 0 62	0.59	1 38	0.63	7.87

Surface roughness: $Ra_{max} = 63 \mu in$

The required grounding rings can be ordered as accessories (order code: DK5HR-****).

1) DN $^1\!\!/_{12}$ to $^3\!\!/_{8}$ with DN $^1\!\!/_{2}"$ flanges as standard


Lap joint flange according to ASME B16.5: Class 150 PVDF Order code for "Process connection", option A4P							
DN A B C D E F L [in] [in] [in] [in] [in] [in] [in]							L [in]
½ to 3/8 1)	3.74	2.36	4 × Ø 0.62	0.59	1.38	0.63	7.87
½ 3.74 2.36 4 × Ø 0.62 0.59 1.38							7.87

Surface roughness: $Ra_{max} = 63 \mu in$ Grounding rings are not necessary.

1) DN $^{1}\!/_{12}$ to $^{3}\!/_{8}$ with DN $^{1}\!/_{2}$ " flanges as standard

Welding nipple

Welding nipple with aseptic gasket seal



A0027510

Welding nipple according to ISO 2037 1.4404 (316L), suitable for pipe ISO 2037 Order code for "Process connection", option IAS							
DN [in]	Suitable for pipe ISO 2037 [in]	A [in]	B [in]	L [in]			
¹ / ₁₂ to ³ / ₈	0.50 × 0.06	0.47	0.39	4.65			
1/2	0.75 × 0.06	0.71	0.63	4.65			
1	1.00 × 0.06	0.98	0.89	4.65			
1 ½	1.50 × 0.05	1.50	1.40	8.66			
2	2.00 × 0.05	2.01	1.91	8.66			
3	3.00 × 0.06	3.00	2.87	8.66			
4	2.50 × 0.08	4.00	3.84	8.66			
5	4.00 × 0.08	5.50	5.34	15.00			


Welding nipple according to ISO 2037 1.4404 (316L), suitable for pipe ISO 2037 Order code for "Process connection", option IAS DN Suitable for pipe ISO 2037 В [in] [in] [in] [in] [in] 6 6.63×0.10 6.63 6.42 15.00

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Welding nipple according to ASME BPE 1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C Order code for "Process connection", option AAS						
DN Suitable for pipe according to ASME BPE A B L [in] [in] [in] [in]						
½12 to 3/8	0.50 × 0.06	0.50	0.35	4.65		
1/2	0.75 × 0.06	0.75	0.63	4.65		
1	1.00 × 0.06	1.00	0.89	4.65		
1 1/2	1.50 × 0.06	1.50	1.37	8.66		
2	2.00 × 0.06	2.00	1.87	8.66		
3	3.00 × 0.06	3.00	2.87	8.66		
4	4.00 × 0.08	4.00	3.83	8.66		
6	6.00 × 0.11	6.00	5.78	11.80		

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Welding nipple with O-ring seal




A0027510

1.4404 (316	Welding nipple according to ISO 1127 1.4404 (316L), suitable for pipe according to ISO 1127 series 1 Order code for "Process connection", option A2S						
DN Suitable for pipe according to ISO 1127 series 1 A B L [in] [in] [in] [in]							
½112 to 3/8	0.53 × 0.09	0.53	0.35	4.99			
1/2	0.84 × 0.10	0.84	0.63	4.99			
Surface rough	Surface roughness: Ra _{max} = 63 μin						

Clamp connections

Clamp connections with aseptic gasket seal



A001562

Tri-Clamp
1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C
Order code for "Process connection", option FAS

DN [in]	Suitable for pipe according to ASME BPE [in]	A [in]	B [in]	L [in]
½12 to 3/8	1/2	1	0.37	5.63
1/2	3/4	1	0.62	5.63
1	1	2	0.87	5.63
1 1/2	1.50 × 0.06	1.98	1.37	8.66
2	2.00 × 0.06	2.52	1.87	8.66
3	3.00 × 0.06	3.58	2.87	8.66
4	4.00 × 0.08	4.68	3.83	8.66
6	6.00 × 0.11	6.57	5.90	11.80

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Clamp according to ISO 2852, Fig. 2
1.4404 (316L)


Order code for "Process connection" ontion IBS

Order code for "Process connection", option IBS					
DN [in]	Suitable for pipe ISO 2037 [in]	DN Clamp ISO 2852 [in]	A [in]	B [in]	L [in]
1	0.96 × 0.06	1	2.00	0.89	6.87
1 ½	1.50 × 0.06	1.50	1.99	1.40	8.66
2	2.00 × 0.06	2.01	2.52	1.91	8.66
3	3.00 × 0.06	3.00	3.58	2.87	8.66
4	2.50 × 0.08	4.00	4.69	3.84	8.66
5	4.00 × 0.08	5.50	6.10	5.34	11.80
6	6.63 × 0.10	6.63	7.20	6.42	11.80

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Couplings

Thread with aseptic gasket seal



A0027509

Coupling DIN 11851, thread
1.4404 (316L), suitable for pipe EN 10357

Order code for "Process connection", option DCS

DN [in]	Suitable for pipe EN 10357 series B [in]	A [in]	B [in]	L [in]
¹ / ₁₂ to ⁵ / ₁₆	0.47 × 0.04 (DN 1/8)	Rd 1.10 × 1/8	0.39	6.85
1/2	0.71 × 0.06	Rd 1.34 × 1/8	0.63	6.85
1	1.10 × 0.04 or 1.10×0.06	Rd 2.05 × ¹ / ₆	1.02	7.48

series B

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling DIN 11851, thread 1.4404 (316L), suitable for pipe EN 10357 series A Order code for "Process connection", option DCS						
DN [in]	Suitable for pipe EN 10357 series A [in]	A [in]	B [in]	L [in]		
1 ½	1.65 × 0.06	Rd 2.56 × 1/ ₆	1.50	10.20		
2	2.13 × 0.06	Rd 3.07 × ¹ / ₆	1.97	10.20		
3	3.35 × 0.08	Rd 4.33 × 1/ ₄	3.19	11.00		
4	4.09 × 0.08	Rd 5.12× 1/4	3.94	11.40		
5	5.08 × 0.08	Rd 6.30 × 1/4	4.92	15.00		
6	6.06 × 0.08	Rd 6.30 × 1/4	5.91	15.40		

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling ISO 2853, thread 1.4404 (316L) Order code for "Process connection", option ICS									
DN [in]	Suitable for pipe EN 10357 (DIN 11850) [in]	DN Clamp ISO 2853 [in]	A [in]	B [in]	L [in]				
1 ½	1.50 × 0.06	1.50	Tr 2.00 × 0.13	1.40	10.80				
2	2.00 × 0.06	2.01	Tr 2.52 × 0.13	1.91	10.80				
3	3.00 × 0.06	3.00	Tr 3.58 × 0.13	2.87	10.90				
4	2.50 × 0.08	4.00	Tr 4.65 × 0.13	3.84	11.30				

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.


Coupling SMS 1145, thread 1.4404 (316L)

Order code for "Process connection", option SAS

DN [in]	Suitable for pipe [in]	DN SMS 1145 [in]	A [in]	B [in]	L [in]
1	1	1	Rd1.57 × 0.17	0.89	5.81
1 ½	1.50 × 0.06	1.50	Rd 2.36 × 1/ ₆	1.37	10.10
2	2.00 × 0.06	2.00	Rd 2.76 × 1/ ₆	1.87	10.10
3	3.00 × 0.06	3.00	Rd 3.86 × ½	2.86	10.90
4	4.00 × 0.08	4.00	Rd 5.20 × 1/ ₆	3.83	11.30

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Thread with O-ring seal




A0027509

External thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I2S								
DN [in]								
½12 to 3/8	R 3%	R 0.40 × 3/8	0.39	6.53				
1/2	R 1/2	R 0.52 × ½	0.63	6.53				
1	R1 R0.66 × 1 0.98 6.69							
Surface roug	yhness: Ra _{max} = 63 μin							

Internal thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I3S								
DN [in]	Suitable for external thread ISO 228/DIN 2999 A B [in] [in]							
½12 to 3/8	Rp 3/8	Rp 0.51 × 3/ ₈	0.35	6.93				
1/2	Rp ½	Rp 0.55 × ½	0.63	6.93				
1 Rp 1 Rp 0.67 × 1 1.07 7.41								
Surface rou	ghness: Ra _{max} = 63 μin							

Adhesive sleeves

Adhesive sleeves with O-ring seal




Adhesive sleeve PVC Order code for "Process connection", option O1V								
DN [in]	Suitable for pipe [in]	A [in]	B [in]	C [in]	D [in]	L [in]		
½12 to 3/8	1/2	2.44	1.52	0.71	0.85	6.42		

Surface roughness: Ra_{max} = 63 μ in The required grounding rings can be ordered as accessories (order code: DK5HR-****).

Mounting kits


Wall mounting kit



Α	В	С	ØD	E	F
[in]	[in]	[in]	[in]	[in]	[in]
5.39	4.33	4.72	0.28	4.92	3.46


Accessories

Weather protection cover



■ 52 Engineering unit mm (in)

Remote display and operating module DKX001




■ 53 Engineering unit mm (in)

External WLAN antenna

The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



■ 54 Engineering unit mm (in)


External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/reception conditions at the transmitter mounting location are poor.




■ 55 Engineering unit mm (in)

Spacer



Order code: DK5HB-****								
DN	di	D1	D2	L				
[in]	[in]	[in]	[in]	[in]				
3	2.87	5.54	5.55	1.30				
4	3.83	6.56	6.38	1.30				

Clamp connections with aseptic gasket seal available for order




56 Hygienic clamp adapter connection suitable for pipes with connection according to ASME BPE (reduction)

Tri-Clamp 1.4404 (316L), suitable for pipe according to ASME BPE and BS 4825, reduction from pipe OD 1" (Tri-Clamp connection) to device DN 15 Order code: DKH**-HF**							
DN [in]	Suitable for pipe according to ASME BPE and BS 4825 (reduction) [in]	A [in]	B [in]	L [in]			
1/2	Pipe OD 1"	2	0.87	5.63			

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Design", option CB: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Couplings with O-ring seal available for order




A0027509

External thread 1.4404 (316L) Order code: DKH**-GD**								
DN [in]	Suitable for internal thread NPT [in]	A [in]	B [in]	L [in]				
½12 to 3/8	NPT 3/8	R 0.61 × 3/8	0.39	7.39				
1/2	NPT ½	R 0.79 × ½	0.63	7.39				
1	NPT 1	R 1 × 1	1.00	7.73				
Surface rough	ness: Ra _{max} = 63 µin							

Internal thread 1.4404 (316L) Order code: DKH**-GC**								
DN [in]	Suitable for external thread NPT [in]	A [in]	B [in]	L [in]				
½12 to 3/8	NPT 3/8	R 0.51 × 3/8	0.35	6.93				
1/2	NPT ½	R 0.55 × ½	0.63	6.93				
1	NPT 1	R 0.67 × 1	1.07	7.41				
Surface roughness: Ra _{max} = 63 μin								

Grounding rings



A00176

For lap joint flange made of PVDF and PVC adhesive sleeve 1.4435 (316L), Alloy C22, tantalum Order code: DK5HR-****									
DN	di	В	С	D	E	F	G	Н	J
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
½12 to 3/8	0.35	0.87	0.69	1.33	0.02	0.14	0.07	0.13	0.18
1/2	0.63	1.14	0.97	1.33	0.02	0.14	0.07	0.13	0.18
1	0.89	1.44	1.23	1.73	0.02	0.14	0.07	0.13	0.18

Weight

All values (weight exclusive of packaging material) refer to devices with flanges of the standard pressure rating.

The weight may be lower than indicated depending on the pressure rating and design.

Weight specifications including transmitter as per order code for "Housing", option A "Aluminum, coated".

Different values due to different transmitter versions:

- Transmitter version for the hazardous area
 - (Order code for "Housing", option A "Aluminum, coated"; Ex d): +2 kg (+4.4 lbs)
- Transmitter version for hygienic area

(Order code for "Housing", option B "Stainless, hygienic"): +0.2 kg (+0.44 lbs)

Nominal	diameter	Weight		
[mm]	[in]	[kg]	[lbs]	
2	1/12	4.7	10.4	
4	5/32	4.7	10.4	
8	5/16	4.7	10.4	
15	1/2	4.6	10.1	

Nominal diameter		Weight	
[mm]	[in]	[kg]	[lbs]
25	1	5.5	12.1
40	1 ½	6.8	15.0
50	2	7.3	16.1
65	-	8.1	17.9
80	3	8.7	19.2
100	4	10.0	22.1
125	5	15.4	34.0
150	6	17.8	39.3

Measuring tube specification

Nominal diameter		Pressure rating ¹⁾ EN (DIN)	Process connection internal diameter PFA	
[mm]	[in]	[bar]	[mm]	[in]
2	1/12	PN 16/40	2.25	0.09
4	5/32	PN 16/40	4.5	0.18
8	5/16	PN 16/40	9.0	0.35
15	1/2	PN 16/40	16.0	0.63
_	1	PN 16/40	22.6 ²⁾	0.89 ²⁾
25	_	PN 16/40	26.0 ³⁾	1.02 3)

- 1) Depending on process connection and seals used
- 2) Order code 5H**22
- 3) Order code 5H**26

Materials

Transmitter housing

Order code for "Housing":

- Option A "Aluminum, coated": aluminum, AlSi10Mg, coated
- Option **B** "Stainless, hygienic": stainless steel, 1.4404 (316L)

Window material

Order code for "Housing":


- Option **A** "Aluminum, coated": glass
- Option **B** "Stainless, hygienic": polycarbonate

Seals

Order code for "Housing":

Option ${\bf B}$ "Stainless, hygienic": EPDM and silicone

Cable entries/cable glands



■ 57 Possible cable entries/cable glands

- 1 Female thread M20 \times 1.5
- 2 Cable gland $M20 \times 1.5$
- 3 Adapter for cable entry with female thread G $\frac{1}{2}$ or NPT $\frac{1}{2}$
- 4 Device plug

Order code for "Housing", option A "Aluminum, coated"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Compression fitting M20 × 1.5	Non-Ex: plastic
Compression many wizo ^ 1.5	Z2, D2, Ex d/de: brass with plastic
Adapter for cable entry with female thread G 1/2"	Nickel-plated brass
Adapter for cable entry with female thread NPT 1/2"	

Order code for "Housing", option B "Stainless, hygienic"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Plastic
Adapter for cable entry with female thread G 1/2"	Nickel-plated brass
Adapter for cable entry with female thread NPT 1/2"	

Device plug

Electrical connection	Material
Plug M12x1	 Socket: Stainless steel, 1.4404 (316L) Contact housing: Polyamide Contacts: Gold-plated brass

Sensor housing

Stainless steel 1.4301 (304)

Measuring tubes

Stainless steel 1.4301 (304)

Liner

PFA (USP Class VI, FDA 21 CFR 177.2600)

Process connections

- Stainless steel, 1.4404 (F316L)
- PVDF
- PVC adhesive sleeve

Electrodes

Standard: 1.4435 (316L)

Seals

- O-ring seal, DN 2 to 25 (1/12 to 1"): EPDM, FKM ²⁾, Kalrez
- Aseptic ³⁾ gasket seal, DN 2 to 150 (1/12 to 6"): EPDM, FKM ²⁾, VMQ (silicone)

Accessories

Protective cover

Stainless steel, 1.4404 (316L)

External WLAN antenna

- Antenna: ASA plastic (acrylic ester-styrene-acrylonitrile) and nickel-plated brass
- Adapter: Stainless steel and nickel-plated brass
- Cable: Polyethylene
- Plug: Nickel-plated brass
- Angle bracket: Stainless steel

Grounding rings

- Standard: 1.4435 (316L)
- Optional: Alloy C22, tantalum

Wall mounting kit

Stainless steel, 1.4301 (304) 4)

Spacer

1.4435 (F316L)

Fitted electrodes

- 2 measuring electrodes for signal detection
- 1 empty pipe detection electrode for empty pipe detection/temperature measurement (only DN 15 to 150 (½ to 6"))

Process connections

With O-ring seal:

- Welding nipple (DIN EN ISO 1127, ODT/SMS, ISO 2037)
- Flange (EN (DIN), ASME, JIS)
- Flange from PVDF (EN (DIN), ASME, JIS)
- External thread
- Internal thread
- Hose connection
- PVC adhesive sleeve

With aseptic molded seal:

- Coupling (DIN 11851, DIN 11864-1, ISO 2853, SMS 1145)
- Flange DIN 11864-2
- i

Surface roughness

Electrodes:

- Stainless steel, 1.4435 (316L) electropolished $\leq 0.5~\mu m$ (19.7 μin)
- Alloy C22, 2.4602 (UNSN06022); tantalum \leq 0.5 μ m (19.7 μ in)

²⁾ USP Class VI, FDA 21 CFR 177.2600, 3A

³⁾ Aseptic means hygienic design in this context

⁴⁾ Does not meet the hygienic design installation guidelines.

(All data refer to parts in contact with the medium)

Liner with PFA: $\leq 0.4 \mu m (15.7 \mu in)$

(All data refer to parts in contact with the medium)

Stainless steel process connections:

- With O-ring seal: $\leq 1.6 \mu m (63 \mu in)$
- With aseptic seal: Ra_{max} = 0.76 μm (31.5 μin)
 Optional: Ra_{max} = 0.38 μm (15 μin) electropolished

(All data refer to parts in contact with the medium)

Operability

Operating concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnostics
- Expert level

Fast and safe commissioning

- Guided menus ("Make-it-run" wizards) for applications
- Menu guidance with brief descriptions of the individual parameter functions
- Access to the device via Web server
- WLAN access to the device via mobile handheld terminal, tablet or smart phone

Reliable operation

- Operation in local language
- Uniform operating philosophy applied to device and operating tools
- If replacing electronic modules, transfer the device configuration via the integrated memory (HistoROM backup) which contains the process and measuring device data and the event logbook. No need to reconfigure.

Efficient diagnostic behavior increases measurement availability

- Troubleshooting measures can be called up via the device and in the operating tools
- Diverse simulation options, logbook for events that occur and optional line recorder functions

Languages

Can be operated in the following languages:

- Via local operation
 English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese,
 Japanese, Korean, Vietnamese, Czech, Swedish
- Via Web browser
 English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese,
 Japanese, Vietnamese, Czech, Swedish
- Via "FieldCare", "DeviceCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese

Local operation


Via display module

Equipment:

- Order code for "Display; operation", option F "4-line, illuminated, graphic display; touch control"
- Order code for "Display; operation", option G "4-line, illuminated, graphic display; touch control + W/I A N"



Information about WLAN interface → 🗎 111



A002678

🖪 58 Operation with touch control

Display elements


- 4-line, illuminated, graphic display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F)
 The readability of the display may be impaired at temperatures outside the temperature range.

Operating elements

- External operation via touch control (3 optical keys) without opening the housing: 🕀, 🖃, 🗉
- Operating elements also accessible in the various zones of the hazardous area

Via remote display and operating module DKX001

- i
- - The remote display and operating module DKX001 is only available for the following housing version: order code for "Housing": option A "Aluminum, coated"
 - The measuring device is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring device. Display or operation at the transmitter is not possible in this case.
 - If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring device display module. Only one display or operation unit may be connected to the transmitter at any one time.



■ 59 Operation via remote display and operating module DKX001

A0026786

Display and operating elements

The display and operating elements correspond to those of the display module $\rightarrow \triangleq 103$.

Housing material

The housing material of the display and operating module DKX001 corresponds to the selected material of the transmitter housing.

Transmitter housing		Remote display and operating module
Order code for "Housing"	Material	Material
Option A "Aluminum, coated"	AlSi10Mg, coated	AlSi10Mg, coated

Cable entry

Corresponds to the choice of transmitter housing, order code for "Electrical connection".

Connecting cable

→ 🖺 49

Dimensions


→ 🖺 82

Remote operation

Via HART protocol


This communication interface is available in device versions with a HART output.

104



■ 60 Options for remote operation via HART protocol (active)

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 Field Xpert SMT70
- 7 VIATOR Bluetooth modem with connecting cable
- 8 Transmitter




A0028746

■ 61 Options for remote operation via HART protocol (passive)

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 Field Xpert SMT70
- 9 VIATOR Bluetooth modem with connecting cable
- 10 Transmitter

Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




 \blacksquare 62 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- *3 Industry network*
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device

Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




 \blacksquare 63 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Measuring device

Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.




■ 64 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Segment coupler PROFIBUS DP/PA
- 5 PROFIBUS PA network
- 6 T-box
- 7 Measuring device

Via Modbus RS485 protocol

This communication interface is available in device versions with a Modbus-RS485 output.




■ 65 Options for remote operation via Modbus-RS485 protocol (active)

- 1 Control system (e.g. PLC)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 3 Transmitter

Via EtherNet/IP network

This communication interface is available in device versions with EtherNet/IP.

Star topology




■ 66 Options for remote operation via EtherNet/IP network: star topology

- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 5 Measuring device

Ring topology

The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).



■ 67 Options for remote operation via EtherNet/IP network: ring topology


- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 5 Measuring device

Via PROFINET network

This communication interface is available in device versions with PROFINET.

108

Star topology




■ 68 Options for remote operation via PROFINET network: star topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Ring topology


The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).



■ 69 Options for remote operation via PROFINET network: ring topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Via APL network



A0046117

■ 70 Options for remote operation via APL network

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch, e.g. Scalance X204 (Siemens)
- 3 Computer with Web browser (e.g. Internet Explorer) for access to integrated Web server or computer with operating tool (e.g. FieldCare or DeviceCare with PROFINET COM DTM or SIMATIC PDM with FDI-Package)
- 4 APL power switch (optional)
- 5 APL field switch
- 6 Measuring device

Service interface


Via service interface (CDI-RJ45)

A point-to-point connection can be established via onsite device configuration. With the housing open, the connection is established directly via the service interface (CDI-RJ45) of the device.



An adapter for RJ45 to the M12 plug is optionally available: Order code for "Accessories", option **NB**: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can be established via an M12 plug without opening the device.



A0027563


■ 71 Connection via service interface (CDI-RJ45)

- 1 Computer with Web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated Web server or with "FieldCare", "DeviceCare" operating tool with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 2 Standard Ethernet connecting cable with RJ45 plug
- 3 Service interface (CDI-RJ45) of the measuring device with access to the integrated Web server

110

Via WLAN interface

The optional WLAN interface is available on the following device version: Order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN"



A0034570

- 1 Transmitter with integrated WLAN antenna
- 2 Transmitter with external WLAN antenna
- 3 LED lit constantly: WLAN reception is enabled on measuring device
- 4 LED flashing: WLAN connection established between operating unit and measuring device
- 5 Computer with WLAN interface and Web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device Web server or with operating tool (e.g. FieldCare, DeviceCare)
- 6 Mobile handheld terminal with WLAN interface and Web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device Web server or operating tool (e.g. FieldCare, DeviceCare)
- 7 Smart phone or tablet (e.g. Field Xpert SMT70)

Function	WLAN: IEEE 802.11 b/g (2.4 GHz) • Access Point with DHCP server (factory setting) • Network
Encryption	WPA2-PSK AES-128 (in accordance with IEEE 802.11i)
Configurable WLAN channels	1 to 11
Degree of protection	IP67
Available antennas	 Internal antenna External antenna (optional) In the event of poor transmission/reception conditions at the place of installation. Available as an accessory → □ 120. Only 1 antenna is active at any one time!
Range	 Internal antenna: typically 10 m (32 ft) External antenna: typically 50 m (164 ft)
Materials (external antenna)	 Antenna: ASA plastic (acrylic ester-styrene-acrylonitrile) and nickel-plated brass Adapter: Stainless steel and nickel-plated brass Cable: Polyethylene Plug: Nickel-plated brass Angle bracket: Stainless steel

Network integration

1 Ne


Network integration is only available for the HART communication protocol.

With the optional "OPC-UA Server" application package, the device can be integrated into an Ethernet network via the service interface (CDI-RJ45 and WLAN) and communicate with OPC-UA clients. If the device is used in this way, IT security must be considered.

 \mathbf{i}

Transmitters with an Ex de approval may ${f not}$ be connected via the service interface (CDI-RJ45)! Order code for "Approval transmitter + sensor", options (Ex de): BB, C2, GB, MB, NB

For permanent access to device data and for device configuration via the Web server, the device is incorporated directly in a network via the service interface (CDI-RJ45). In this way, the device can be accessed any time from the control station. The measured values are processed separately via the inputs and outputs through the automation system.



A0033618

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch
- 3 Edge Gateway
- 4 Cloud
- 5 Measuring device
- 6 Ethernet network
- 7 Measured values via inputs and outputs
- 8 Optional WLAN interface
- The optional WLAN interface is available on the following device version:
 Order code for "Display; operation", option **G** "4-line, backlit, graphic display; touch control + WLAN"

Supported operating tools

Different operating tools can be used for local or remote access to the measuring device. Depending on the operating tool used, access is possible with different operating units and via a variety of interfaces.

Supported operating tools	Operating unit	Interface	Additional information
Web browser	Notebook, PC or tablet with Web browser	 CDI-RJ45 service interface WLAN interface Ethernet-based fieldbus (EtherNet/IP, PROFINET) 	Special Documentation for the device
DeviceCare SFE100	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🖺 123
FieldCare SFE500	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🖺 123

Supported operating tools	Operating unit	Interface	Additional information
Field Xpert	SMT70/77/50	All fieldbus protocolsWLAN interfaceBluetoothCDI-RJ45 service interface	Operating Instructions BA01202S Device description files: Use update function of handheld terminal
SmartBlue app	Smart phone or tablet with iOs or Android	WLAN	→ 🖺 123



Other operating tools based on FDT technology with a device driver such as DTM/iDTM or DD/EDD can be used for device operation. These operating tools are available from the individual manufacturers. Integration into the following operating tools, among others, is supported:

- FactoryTalk AssetCentre (FTAC) from Rockwell Automation → www.rockwellautomation.com
- Process Device Manager (PDM) from Siemens → www.siemens.com
- Asset Management Solutions (AMS) from Emerson → www.emersonprocess.com
- FieldCommunicator 375/475 from Emerson → www.emersonprocess.com
- Field Device Manager (FDM) from Honeywell → www.process.honeywell.com
- FieldMate from Yokogawa → www.yokogawa.com
- PACTWare → www.pactware.com

The related device description files are available: www.endress.com → Downloads

Web server

Thanks to the integrated Web server the device can be operated and configured via a Web browser and via the service interface (CDI-RJ45) or via the WLAN interface. The structure of the operating menu is the same as for the local display. In addition to the measured values, device status information is also displayed and allows users to monitor the status of the device. Furthermore the device data can be managed and the network parameters can be configured.

A device that has a WLAN interface (can be ordered as an option) is required for the WLAN connection: order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN". The device acts as an Access Point and enables communication by computer or a mobile handheld terminal.

Supported functions

Data exchange between the operating unit (such as a notebook for example) and the measuring device:

- Upload the configuration from the measuring device (XML format, configuration backup)
- Save the configuration to the measuring device (XML format, restore configuration)
- Export event list (.csv file)
- Export parameter settings (.csv file or PDF file, document the measuring point configuration)
- Export the Heartbeat verification log (PDF file, only available with the "Heartbeat Verification" application package)
- Flash firmware version for device firmware upgrade, for instance
- Download driver for system integration
- Visualize up to 1000 saved measured values (only available with the Extended HistoROM application package →

 119)



Web server special documentation $\rightarrow \implies 125$

HistoROM data management

The measuring device features HistoROM data management. HistoROM data management comprises both the storage and import/export of key device and process data, making operation and servicing far more reliable, secure and efficient.



When the device is delivered, the factory settings of the configuration data are stored as a backup in the device memory. This memory can be overwritten with an updated data record, for example after commissioning.

Additional information on the data storage concept

There are different types of data storage units in which device data are stored and used by the device:

	HistoROM backup	T-DAT	S-DAT
Available data	 Event logbook such as diagnostic events for example Parameter data record backup Device firmware package Driver for system integration for exporting via Web server, e.g: GSD for PROFIBUS DP GSD for PROFIBUS PA GSDML for PROFINET EDS for EtherNet/IP DD for FOUNDATION Fieldbus 	 Measured value logging ("Extended HistoROM" order option) Current parameter data record (used by firmware at run time) Maximum indicators (min/max values) Totalizer values 	 Sensor data: nominal diameter etc. Serial number Calibration data Device configuration (e.g. SW options, fixed I/O or multi I/O)
Storage location	Fixed on the user interface board in the connection compartment	Attachable to the user interface board in the connection compartment	In the sensor plug in the transmitter neck part

Data backup

Automatic

- The most important device data (sensor and transmitter) are automatically saved in the DAT modules
- If the transmitter or measuring device is replaced: once the T-DAT containing the previous device data has been exchanged, the new measuring device is ready for operation again immediately without any errors
- If the sensor is replaced: once the sensor has been replaced, new sensor data are transferred from the S-DAT in the measuring device and the measuring device is ready for operation again immediately without any errors
- If exchanging the electronics module (e.g. I/O electronics module): Once the electronics module has been replaced, the software of the module is compared against the current device firmware. The module software is upgraded or downgraded where necessary. The electronics module is available for use immediately afterwards and no compatibility problems occur.

Manual

Additional parameter data record (complete parameter settings) in the integrated device memory HistoROM backup for:

- Data backup function
 Backup and subsequent restoration of a device configuration in the device memory HistoROM backup
- Data comparison function
 Comparison of the current device configuration with the device configuration saved in the device memory HistoROM backup

Data transmission

Manual

- Transfer of a device configuration to another device using the export function of the specific operating tool, e.g. with FieldCare, DeviceCare or Web server: to duplicate the configuration or to store in an archive (e.g. for backup purposes)
- Transmission of the drivers for system integration via Web server, e.g.:
 - GSD for PROFIBUS DP
 - GSD for PROFIBUS PA
 - GSDML for PROFINET
 - EDS for EtherNet/IP
 - DD for FOUNDATION Fieldbus

Event list

Automatic

- Chronological display of up to 20 event messages in the events list
- If the Extended HistoROM application package (order option) is enabled: up to 100 event messages are displayed in the events list along with a time stamp, plain text description and remedial measures
- The events list can be exported and displayed via a variety of interfaces and operating tools e.g. DeviceCare, FieldCare or Web server

Data logging

Manual

If the **Extended HistoROM** application package (order option) is enabled:

- Record up to 1000 measured values via 1 to 4 channels
- User configurable recording interval
- Record up to 250 measured values via each of the 4 memory channels
- Export the measured value log via a variety of interfaces and operating tools e.g. FieldCare, DeviceCare or web server

Certificates and approvals

Current certificates and approvals that are available for the product can be selected via the Product Configurator at www.endress.com:

- 1. Select the product using the filters and search field.
- 2. Open the product page.
- Select Configuration.

CE mark

The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.

Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

UKCA marking

The device meets the legal requirements of the applicable UK regulations (Statutory Instruments). These are listed in the UKCA Declaration of Conformity along with the designated standards. By selecting the order option for UKCA marking, Endress+Hauser confirms a successful evaluation and testing of the device by affixing the UKCA mark.

Contact address Endress+Hauser UK: Endress+Hauser Ltd.

Floats Road Manchester M23 9NF


United Kingdom www.uk.endress.com

RCM mark

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



ATEX, IECEx

Currently, the following versions for use in hazardous areas are available:

Ex db eb

Category	Type of protection
II2G	Ex db eb ia IIC T6T1 Gb

Ex tb

Category	Type of protection
II2D	Ex tb IIIC Txxx Db

Ех ес

Category	Type of protection
II3G	Ex ec ic IIC T5T1 Gc

cCSAus

Currently, the following versions for use in hazardous areas are available:

IS (Ex i) and XP (Ex d)

Class I, II, III Division 1 Groups A-G

NI (Ex nA)

Class I Division 2 Groups A - D

Ex de

Class I, Zone 1 AEx/ Ex de ia IIC T6...T1 Gb

Fx n A

Class I, Zone 2 AEx/Ex nA ic IIC T5...T1 Gc

Ex th

Zone 21 AEx/ Ex tb IIIC T** ℃ Db

Sanitary compatibility

- 3-A SSI 28-06 or more recent
 - Confirmation by affixing the 3-A logo for measuring devices with the order code for "Additional approval", option LP "3-A".
 - The 3-A approval refers to the measuring device.
 - When installing the measuring device, ensure that no liquid can accumulate on the outside of the measuring device.

Remote transmitters must be installed in accordance with the 3-A Standard.

 Accessories (e.g. weather protection cover, wall holder unit) must be installed in accordance with the 3-A Standard.

Each accessory can be cleaned. Disassembly may be necessary under certain circumstances.

- EHEDG Type EL Class I
 - Confirmation by affixing the EHEDG symbol for measuring devices with the order code for "Additional approval", option LT "EHEDG".
 - EPDM is not a suitable seal material for fluids with a fat content > 8 %.
 - To meet the requirements for EHEDG certification, the device must be used with process connections in accordance with the EHEDG position paper entitled "Easy Cleanable Pipe Couplings and Process Connections" (www.ehedg.org).
- FDA 21 CFR 177
- Food Contact Materials Regulation (EC) 1935/2004
- Food Contact Materials Regulation China GB 4806
- Pasteurized Milk Ordinance (PMO)

Pharmaceutical compatibility

- FDA 21 CFR 177
- USP <87>
- USP <88> Class VI 121 °C
- TSE/BSE Certificate of Suitability
- cGMF

Devices with the order code for "Test, certificate", option JG "Conformity with cGMP-derived requirements, declaration" comply with the requirements of cGMP with regard to the surfaces of parts in contact with the medium, design, FDA 21 CFR material conformity, USP Class VI tests and TSE/BSE conformity.

 $\label{lem:continuous} A \ serial \ number-specific \ declaration \ is \ generated.$

Functional safety

The measuring device can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture; order code for "Additional approval", option LA) and SIL 3 (multichannel architecture with homogeneous redundancy) and is independently evaluated and certified in accordance with IEC 61508.

The following types of monitoring in safety equipment are possible:



Functional Safety Manual with information on the SIL device $\rightarrow~\cong~124$

HART certification

HART interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability)

FOUNDATION Fieldbus certification

FOUNDATION Fieldbus interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified in accordance with FOUNDATION Fieldbus H1
- Interoperability Test Kit (ITK), revision version 6.2.0 (certificate available on request)
- Physical Layer Conformance Test
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFIBUS

PROFIBUS interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V./ PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

EtherNet/IP certification

The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with the ODVA Conformance Test
- EtherNet/IP Performance Test
- EtherNet/IP PlugFest compliance
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFINET

PROFINET interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V. / PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
 - Test specification for PROFINET devices
 - PROFINET Security Level 2 Netload Class 2 0 Mbps
- The device can also be operated with certified devices of other manufacturers (interoperability)
- The device supports PROFINET S2 system redundancy.

Certification PROFINET with Ethernet-APL

PROFINET interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V. / PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
 - Test specification for PROFINET devices
 - PROFINET PA Profile 4
 - PROFINET Security Level 2 Netload Class 2 0 Mbps
 - APL conformance test
- The device can also be operated with certified devices of other manufacturers (interoperability)
- The device supports PROFINET S2 system redundancy.

Radio approval

The measuring device has radio approval.



For detailed information on the radio approval, see the Special Documentation

Pressure Equipment Directive

The devices can be ordered with or without a PED or UKCA approval. If a device with a PED or UKCA approval is required, this must be explicitly stated in the order. For devices with nominal diameters

less than or equal to DN 25 (1"), this is neither possible nor necessary. A UK Ex approval must be selected for UKCA.

- With the marking:
 - a) PED/G1/x (x = category) or
 - b) UK/G1/x (x = category)

on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements"

- a) specified in Annex I of the Pressure Equipment Directive 2014/68/EU or
- b) Schedule 2 of Statutory Instruments 2016 No. 1105.
- Devices bearing this marking (PED or UKCA) are suitable for the following types of medium: Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to 0.5 bar (7.3 psi)
- Devices not bearing this marking (without PED or UKCA) are designed and manufactured according to sound engineering practice. They meet the requirements of
 - a) Art. 4 Para. 3 of the Pressure Equipment Directive 2014/68/EU or
 - b) Part 1, Para. 8 of Statutory Instruments 2016 No. 1105.

The scope of application is indicated

- a) in diagrams 6 to 9 in Annex II of the Pressure Equipment Directive 2014/68/EU or
- b) Schedule 3, Para. 2 of Statutory Instruments 2016 No. 1105.

Additional certification

PWIS-free

PWIS = paint-wetting impairment substances

Order code for "Service":

- Option **HC**: PWIS-free (version A)
- Option **HD**: PWIS-free (version B)
- Option **HE**: PWIS-free (version C)



For more information on PWIS-free certification, see "Test specification" document TS01028D

Other standards and guidelines

■ EN 60529

Degrees of protection provided by enclosures (IP code)

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements

■ IEC/EN 61326-2-3

Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).

■ NAMUR NE 21

 $Electromagnetic \ compatibility \ (EMC) \ of \ industrial \ process \ and \ laboratory \ control \ equipment$

NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

■ NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices

■ NAMUR NE 107

Self-monitoring and diagnosis of field devices

NAMUR NE 131

Requirements for field devices for standard applications

■ ETSI EN 300 328

Guidelines for 2.4 GHz radio components.

■ EN 301489

Electromagnetic compatibility and radio spectrum matters (ERM).

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

- 1. Select the product using the filters and search field.
- 2. Open the product page.
- 3. Select **Configuration**.

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Diagnostic functionality

Order code for "Application package", option EA "Extended HistoROM"

Comprises extended functions concerning the event log and the activation of the measured value memory.

Event log:

Memory volume is extended from 20 message entries (standard version) to up to 100 entries.

Data logging (line recorder):

- Memory capacity for up to 1000 measured values is activated.
- 250 measured values can be output via each of the 4 memory channels. The recording interval can
 be defined and configured by the user.
- Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server.



For detailed information, see the Operating Instructions for the device.

Heartbeat Technology

Order code for "Application package", option EB "Heartbeat Verification + Monitoring"

Heartbeat Verification

Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment".

- $\ \ \blacksquare$ Functional testing in the installed state without interrupting the process.
- Traceable verification results on request, including a report.
- Simple testing process via local operation or other operating interfaces.
- Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.
- Extension of calibration intervals according to operator's risk assessment.

Heartbeat Monitoring

Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to:

- Draw conclusions using these data and other information about the impact the process influences (e.g. formation of buildup, magnetic field interference etc.) have on measuring performance over time.
- Schedule servicing in time.
- Monitor the process or product quality.



For detailed information, see the Special Documentation for the device.

Cleaning

Order code for "Application package", option EC "ECC electrode cleaning"

The electrode cleaning circuit (ECC) function has been developed to have a solution for applications where magnetite (Fe_3O_4) deposits frequently occur (e.g. hot water). Since magnetite is highly conductive this build up leads to measuring errors and ultimately to the loss of signal. The application package is designed to avoid build-up of very conductive matter and thin layers (typical of magnetite).



For detailed information, see the Operating Instructions for the device.

OPC-UA Server

Order code for "Application package", option EL "OPC-UA Server"

The application package provides an integrated OPC-UA server for comprehensive device services for IoT and SCADA applications.



For detailed information, see the Special Documentation for the device.

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the transmitter

Accessories	Description
Proline 300 transmitter	Transmitter for replacement or storage. Use the order code to define the following specifications: Approvals Output Input Display/operation Housing Software Order code: 5X3BXX Installation Instructions EA01199D

Remote display and operating module DKX001	 If ordered directly with the measuring device: Order code for "Display; operation", option O "Remote display 4-line, illuminated; 10 m (30 ft) cable; touch control" If ordered separately: Measuring device: order code for "Display; operation", option M "W/o, prepared for remote display" DKX001: Via the separate product structure DKX001 If ordered subsequently: DKX001: Via the separate product structure DKX001
	Mounting bracket for DKX001 ■ If ordered directly: order code for "Accessory enclosed", option RA "Mounting bracket, pipe 1/2" ■ If ordered subsequently: order number: 71340960
	Connecting cable (replacement cable) Via the separate product structure: DKX002
	Further information on display and operating module DKX001 \rightarrow $\stackrel{\triangle}{=}$ 104.
	Special Documentation SD01763D
External WLAN antenna	External WLAN antenna with 1.5 m (59.1 in) connecting cable and two angle brackets. Order code for "Accessory enclosed", option P8 "Wireless antenna wide area".
	The external WLAN antenna is not suitable for use in hygienic applications.
	• Additional information regarding the WLAN interface $\rightarrow riangleq riangle$
	Order number: 71351317
	Installation Instructions EA01238D
Weather protection cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight.
	① Order number: 71343505
	Installation Instructions EA01160D

For the sensor

Accessories	Description
Adapter set	Adapter connections for installing a Promag H instead of a Promag 30/33 A or Promag 30/33 H (DN 25).
	Consists of: 2 process connections Screws Seals
Seal set	For the regular replacement of seals for the sensor.
Spacer	If replacing a DN $80/100$ sensor in an existing installation, a spacer is needed if the new sensor is shorter.
Welding jig	Welding socket as process connection: welding jig for installation in pipe.
Grounding rings	Are used to ground the medium in lined measuring tubes to ensure proper measurement.
	Grounding rings can be ordered via the device order structure or configured and ordered as an accessory via the DK5HR order structure.
Mounting kit	Consists of: 2 process connections Screws Seals
Wall mounting kit	Wall mounting kit for measuring device (only DN 2 to 25 (1/12 to 1"))

Communication-specific accessories

Accessories	Description
Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. Technical Information TI00404F
HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. Technical Information TI00429F Operating Instructions BA00371F
Fieldgate FXA42	Is used to transmit the measured values of connected 4 to 20 mA analog measuring devices, as well as digital measuring devices Technical Information TI01297S Operating Instructions BA01778S Product page: www.endress.com/fxa42
Field Xpert SMT50	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.
	 Technical Information TI01342S Operating Instructions BA01709S Product page: www.endress.com/smt50
Field Xpert SMT70	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle. Technical Information TI01342S Operating Instructions BA01709S
Field Xpert SMT77	 Product page: www.endress.com/smt70 The Field Xpert SMT77 tablet PC for device configuration enables mobile plant
rielu Apert Sivi1//	asset management in areas categorized as Ex Zone 1. Technical Information TI01418S Operating Instructions BA01923S Product page: www.endress.com/smt77

Service-specific accessories

Accessory	Description
Applicator	Software for selecting and sizing Endress+Hauser measuring devices: Choice of measuring devices with industrial requirements Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy. Graphic illustration of the calculation results Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.
	Applicator is available: • Via the Internet: https://portal.endress.com/webapp/applicator • As a downloadable DVD for local PC installation.
W@M	W@M Life Cycle Management Improved productivity with information at your fingertips. Data relevant to a plant and its components is generated from the first stages of planning and during the asset's complete life cycle. W@M Life Cycle Management is an open and flexible information platform with online and on-site tools. Instant access for your staff to current, in-depth data shortens your plant's engineering time, speeds up procurement processes and increases plant uptime. Combined with the right services, W@M Life Cycle Management boosts productivity in every phase. For more information, see: www.endress.com/lifecyclemanagement
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition. Operating Instructions BA00027S and BA00059S
DeviceCare	Tool for connecting and configuring Endress+Hauser field devices. Innovation brochure IN01047S

System components

Accessories	Description
Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.
	Technical Information TI00133ROperating Instructions BA00247R
iTEMP	The temperature transmitters can be used in all applications and are suitable for the measurement of gases, steam and liquids. They can be used to read in the medium temperature.
	"Fields of Activity" document FA00006T

Supplementary documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- Device Viewer (www.endress.com/deviceviewer): Enter serial number from nameplate.
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

Standard documentation

Brief Operating Instructions

Brief Operating Instructions for the sensor

Measuring device	Documentation code
Proline Promag H	KA01289D

Brief Operating Instructions for the transmitter

	Documentation code							
Measuring device	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Proline 300	KA01308D	KA01294D	KA01405D	KA01385D	KA01310D	KA01338D	KA01340D	KA01516D

Operating Instructions

Measuring device	Documentation	Documentation code						
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Promag H 300	BA01392D	BA01477D	BA01396D	BA01865D	BA01394D	BA01716D	BA01718D	BA02106D

Description of Device Parameters

Measuring device	Documentatio	Documentation code						
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Promag 300	GP01051D	GP01098D	GP01052D	GP01135D	GP01053D	GP01113D	GP01112D	GP01172D

Supplementary devicedependent documentation Safety instructions

Safety instructions for electrical equipment for hazardous areas.

Contents	Documentation code
ATEX/IECEx Ex d/Ex de	XA01414D
ATEX/IECEx Ex ec	XA01514D
cCSAus XP	XA01515D
cCSAus Ex d/ Ex de	XA01516D
cCSAus Ex nA	XA01517D
INMETRO Ex d/Ex de	XA01518D
INMETRO Ex ec	XA01519D
NEPSI Ex d/Ex de	XA01520D
NEPSI Ex nA	XA01521D
EAC Ex d/Ex de	XA01656D
EAC Ex nA	XA01657D
JPN Ex d	XA01775D

Remote display and operating module DKX001

Contents	Documentation code
ATEX/IECEx Ex i	XA01494D
ATEX/IECEx Ex ec	XA01498D
cCSAus IS	XA01499D
cCSAus Ex nA	XA01513D

Contents	Documentation code
INMETRO Ex i	XA01500D
INMETRO Ex ec	XA01501D
NEPSI Ex i	XA01502D
NEPSI Ex nA	XA01503D

Functional Safety Manual

Contents	Documentation code
Promag 300	SD01740D

Special Documentation

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01614D
Radio approvals for WLAN interface for A309/A310 display module	SD01793D
Remote display and operating module DKX001	SD01763D
OPC-UA server ¹⁾	SD02043D

1) This Special Documentation is only available for device versions with a HART output.

Contents	Documentatio	Documentation code						
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	PROFINET	EtherNet/IP	PROFINET with Ethernet- APL
Heartbeat Technology	SD01640D	SD01742D	SD01744D	SD02206D	SD01743D	SD01986D	SD01980D	SD02729D
Web server	SD01654D	SD01657D	SD01656D	SD02235D	SD01655D	SD01977D	SD01976D	SD02768D

Installation Instructions

Contents	Comment
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory \rightarrow $\ \ \ \ \ \ \ \ \ $

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

PROFIBUS®

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

FOUNDATION™ Fieldbus

Registration-pending trademark of the FieldComm Group, Austin, Texas, USA

Modbus[®]

Registered trademark of SCHNEIDER AUTOMATION, INC.

EtherNet/IP™

Trademark of ODVA, Inc.

Ethernet-APL TM

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

PROFINET®

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA



www.addresses.endress.com

