Technical Information **Proline Promag 10W**

Electromagnetic flowmeter

Products



Sensor with degree of protection IP68 (Type 6P enclosure) with a highly cost-effective transmitter

Application

- The bidirectionally measuring principle is virtually independent of pressure, density, temperature and viscosity
- The specialist in the water and wastewater industry for the most demanding applications

Device properties

- International drinking water approvals
- Degree of protection IP68 (Type 6P enclosure)
- 2-line display with push buttons
- Device in compact or remote version
- HART

Your benefits

- Secure, reliable long-term operation robust and completely welded sensor
- Energy-saving flow measurement no pressure loss due to cross-section constriction
- Maintenance-free no moving parts
- Cost-effective designed for easy applications and direct integration
- Safe operation display provides easy readable process information
- Fully industry compliant IEC/EN/NAMUR



Table of contents

Function and system design	
Measuring principle	
Measuring system	3
Input	/ 1
<u>-</u>	
Measured variable	
Measuring ranges	
Operable flow range	6
Output	7
Output signal	
Signal on alarm	7
Load	
Low flow	
Galvanic isolation	7
Power supply	8
Terminal assignment	Ω
Supply voltage	
Power consumption	
Power supply failure	
Electrical connection	
Electrical connection, remote version	
Potential equalization	
Cable entry 1	0
Remote version cable specifications	
· ·	
	_
D (1 , 1 , 1)	
Performance characteristics	
Reference operating conditions 1	2
	2
Reference operating conditions 1 Maximum measured error 1	2
Reference operating conditions 1	2
Reference operating conditions 1 Maximum measured error 1 Repeatability 1	2 2 2
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1	2 2 2
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1	2 2 2 3
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1	2 2 2 3 4
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1	2 2 2 3 4 5
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1	2 2 2 3 4 5
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1	2 2 3 3 4 5 6
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1	2 2 3 3 4 5 6
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1	2 2 3 3 4 5 6 6
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1	2 2 3 3 4 5 6 6
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1	2 2 3 3 4 5 6 6 7 7
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1	2 2 2 3 3 4 5 6 6 7 7 7
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1	222 3 34566 7 777
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1	222 3 34566 7 777
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1	222 3 34566 7 7777
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Storage temperature range 1 Degree of protection 1 Shock and vibration resistance 1	222 3 34566 7 7777
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1	222 3 34566 7 77777
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1 Process 1	222 3 34566 7 77777 8
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Storage temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1 Process 1 Medium temperature range 1 Index of the storage 1 Medium temperature range 1 Medium temperature range 1 Index of the storage 1 Index of the stor	222 3 34566 7 77777 8 8
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1 Process 1 Medium temperature range 1 Conductivity 1	222 3 34566 7 77777 8 88
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1 Process 1 Medium temperature range 1 Conductivity 1 Pressure-temperature ratings 1	2 2 2 3 3 4 5 6 6 7 7 7 7 7 8 8 8 8 8 8
Reference operating conditions	2 2 2 3 3 4 5 6 6 7 7 7 7 7 8 8 8 8 8 8
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1 Process 1 Medium temperature range 1 Conductivity 1 Pressure-temperature range (nominal pressure) 2 Pressure tightness 2	2 2 2 3 3 4 5 5 6 6 7 7 7 7 7 8 8 8 8 1 1
Reference operating conditions	2 2 2 3 3 4 5 5 6 6 7 7 7 7 7 8 8 8 8 1 1
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1 Process 1 Medium temperature range 1 Conductivity 1 Pressure-temperature range (nominal pressure) 2 Pressure tightness 2	2 2 2 3 3 4 4 5 6 6 6 7 7 7 7 7 8 8 8 8 8 1 1 1 1
Reference operating conditions 1 Maximum measured error 1 Repeatability 1 Installations 1 Mounting location 1 Orientation 1 Inlet and outlet run 1 Adapters 1 Length of connecting cable 1 Environment 1 Ambient temperature range 1 Storage temperature 1 Degree of protection 1 Shock and vibration resistance 1 Electromagnetic compatibility (EMC) 1 Process 1 Medium temperature range 1 Conductivity 1 Pressure-temperature range (nominal pressure) 2 Pressure tightness 2 Limiting flow 2	2 2 2 3 3 4 4 5 6 6 7 7 7 7 7 8 8 8 8 1 1 1 1 1


Mechanical construction	.3
Design, dimensions	23
Weight	
Measuring tube specifications	37
Material 3	
Fitted electrodes 3	
Process connections 3	
Surface roughness	38
Operability	8
Local operation 3	38
Remote operation	39
Certificates and approvals	39
CE mark 3	
C-tick mark 3	39
Ex approval	
Other standards and guidelines	
Pressure equipment directive	39
Ordering information	9
Accessories4	ŧС
Device-specific accessories	
Communication-specific accessories	
Service-specific accessories	
Documentation 4	·2
Registered trademarks4	·2

Function and system design

Measuring principle

Following Faraday's law of magnetic induction, a voltage is induced in a conductor moving through a magnetic field.

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced is proportional to the flow velocity and is supplied to the amplifier by means of two measuring electrodes. The flow volume is calculated by means of the pipe cross-sectional area. The DC magnetic field is created through a switched direct current of alternating polarity.



 $Ue = B \cdot L \cdot v$ $Q = A \cdot v$

Uе Induced voltage

Magnetic induction (magnetic field)

B L Electrode spacing Flow velocity Volume flow Pipe cross-section Current strength

Measuring system

The measuring system consists of a transmitter and a sensor.

Two versions are available:

- Compact version: Transmitter and sensor form a mechanical unit.
- Remote version: Sensor is mounted separate from the transmitter.

Transmitter:

• Promag 10 (key operation, two-line, unilluminated display)

Promag W, DN 25 to 2000 (1 to 78")

Input

Measured variable

Flow velocity (proportional to induced voltage)

Measuring ranges

Typically v = 0.01 to 10 m/s (0.033 to 33 ft/s) with the specified accuracy

Standard version

Flow ch	Flow characteristic values (SI units)										
Dian	neter	Recommende	ed flow			Factory sett	ings				
		Min./max. full sca	le value	Current	le value : output	Pulse va	alue	Lo	w flow		
[mm]	[inch]	(v ~ 0.3 or 10 m/s)	(v ~ 2.	5 m/s)	(~ 2 puls	ses/s)	(v ~ C	0.04 m/s)		
25	1"	9 to 300	dm³/min	75	dm³/min	0.50	dm³	1	dm³/min		
32	-	15 to 500	dm³/min	125	dm³/min	1.00	dm ³	2	dm³/min		
40	1½"	25 to 700	dm³/min	200	dm³/min	1.50	dm ³	3	dm³/min		
50	2"	35 to 1100	dm³/min	300	dm³/min	2.50	dm³	5	dm³/min		
65	_	60 to 2000	dm³/min	500	dm³/min	5.00	dm ³	8	dm³/min		
80	3"	90 to 3000	dm³/min	750	dm³/min	5.00	dm^3	12	dm³/min		
100	4"	145 to 4700	dm^3/min	1200	dm³/min	10.00	$dm^{3} \\$	20	dm³/min		
125	-	220 to 7500	dm³/min	1850	dm³/min	15.00	dm^3	30	dm³/min		
150	6"	20 to 600	m³/h	150	m³/h	0.025	m³	2.5	m³/h		
200	8"	35 to 1100	m³/h	300	m³/h	0.05	m^3	5.0	m³/h		
250	10"	55 to 1700	m³/h	500	m³/h	0.05	m^3	7.5	m³/h		
300	12"	80 to 2400	m³/h	750	m³/h	0.10	m^3	10	m³/h		
350	14"	110 to 3300	m³/h	1000	m³/h	0.10	m^3	15	m³/h		
375	15"	140 to 4200	m³/h	1200	m³/h	0.15	m^3	20	m³/h		
400	16"	140 to 4200	m³/h	1200	m³/h	0.15	m ³	20	m³/h		
450	18"	180 to 5400	m³/h	1500	m³/h	0.25	m³	25	m³/h		
500	20"	220 to 6600	m³/h	2000	m³/h	0.25	m ³	30	m³/h		
600	24"	310 to 9600	m³/h	2500	m³/h	0.30	m ³	40	m³/h		
700	28"	420 to 13500	m³/h	3500	m³/h	0.50	m³	50	m³/h		
-	30"	480 to 15000	m³/h	4000	m³/h	0.50	m ³	60	m³/h		
800	32"	550 to 18000	m³/h	4500	m³/h	0.75	m ³	75	m³/h		
900	36"	690 to 22500	m³/h	6000	m³/h	0.75	m³	100	m³/h		
1000	40"	850 to 28000	m³/h	7000	m³/h	1.00	m ³	125	m³/h		
-	42"	950 to 30000	m³/h	8000	m³/h	1.00	m ³	125	m³/h		
1200	48"	1250 to 40000	m³/h	10000	m³/h	1.50	m ³	150	m³/h		
_	54"	1550 to 50000	m³/h	13000	m³/h	1.50	m ³	200	m³/h		
1400	-	1700 to 55000	m³/h	14000	m³/h	2.00	m ³	225	m³/h		
_	60"	1950 to 60000	m³/h	16000	m³/h	2.00	m ³	250	m³/h		
1600	-	2200 to 70000	m³/h	18000	m³/h	2.50	m ³	300	m³/h		
-	66"	2500 to 80000	m³/h	20500	m³/h	2.50	m ³	325	m³/h		
1800	72"	2800 to 90000	m³/h	23000	m³/h	3.00	m ³	350	m³/h		
-	78"	3300 to 100000	m³/h	28500	m³/h	3.50	m ³	450	m³/h		
2000	_	3400 to 110000		28500		3.50			m³/h		

Flow ch	naracteri	istic values (US un	its)						
Dian	neter	Recommended	flow rate		:	Factory sett	ings		
		Min./max. full s	cale value		le value	Pulse v	alue	Lo	w flow
[inch]	[mm]	(v ~ 0.3 or 10	O m/s)		5 m/s)	(~ 2 puls	ses/s)	(v ~ 0	0.04 m/s)
1"	25	2.5 to 80	gal/min	18	gal/min	0.20	gal	0.25	gal/min
-	32	4 to 130	gal/min	30	gal/min	0.20	gal	0.50	gal/min
1½"	40	7 to 190	gal/min	50	gal/min	0.50	gal	0.75	gal/min
2"	50	10 to 300	gal/min	75	gal/min	0.50	gal	1.25	gal/min
-	65	16 to 500	gal/min	130	gal/min	1	gal	2.0	gal/min
3"	80	24 to 800	gal/min	200	gal/min	2	gal	2.5	gal/min
4"	100	40 to 1250	gal/min	300	gal/min	2	gal	4.0	gal/min
-	125	60 to 1950	gal/min	450	gal/min	5	gal	7.0	gal/min
6"	150	90 to 2650	gal/min	600	gal/min	5	gal	12	gal/min
8"	200	155 to 4850	gal/min	1200	gal/min	10	gal	15	gal/min
10"	250	250 to 7500	gal/min	1500	gal/min	15	gal	30	gal/min
12"	300	350 to 10600	gal/min	2400	gal/min	25	gal	45	gal/min
14"	350	500 to 15000	gal/min	3600	gal/min	30	gal	60	gal/min
15"	375	600 to 19000	gal/min	4800	gal/min	50	gal	60	gal/min
16"	400	600 to 19000	gal/min	4800	gal/min	50	gal	60	gal/min
18"	450	800 to 24000	gal/min	6000	gal/min	50	gal	90	gal/min
20"	500	1000 to 30000	gal/min	7500	gal/min	75	gal	120	gal/min
24"	600	1400 to 44000	gal/min	10500	gal/min	100	gal	180	gal/min
28"	700	1900 to 60000	gal/min	13500	gal/min	125	gal	210	gal/min
30"	1	2150 to 67000	gal/min	16500	gal/min	150	gal	270	gal/min
32"	800	2450 to 80000	gal/min	19500	gal/min	200	gal	300	gal/min
36"	900	3100 to 100000	gal/min	24000	gal/min	225	gal	360	gal/min
40"	1000	3800 to 125000	gal/min	30000	gal/min	250	gal	480	gal/min
42"	-	4200 to 135000	gal/min	33000	gal/min	250	gal	600	gal/min
48"	1200	5500 to 175000	gal/min	42000	gal/min	400	gal	600	gal/min
54"	ı	9 to 300	Mgal/min	75	Mgal/min	0.0005	Mgal	1.3	Mgal/min
-	1400	10 to 340	Mgal/min	85	Mgal/min	0.0005	Mgal	1.3	Mgal/min
60"	ı	12 to 380	Mgal/min	95	Mgal/min	0.0005	Mgal	1.3	Mgal/min
-	1600	13 to 450	Mgal/min	110	Mgal/min	0.0008	Mgal	1.7	Mgal/min
66"	ı	14 to 500	Mgal/min	120	Mgal/min	0.0008	Mgal	2.2	Mgal/min
72"	1800	16 to 570	Mgal/min	140	Mgal/min	0.0008	Mgal	2.6	Mgal/min
78"	-	18 to 650	Mgal/min	175	Mgal/min	0.001	Mgal	3.0	Mgal/min
-	2000	20 to 700	Mgal/min	175	Mgal/min	0.001	Mgal	3.0	Mgal/min

Optional version w/o inlet and outlet runs

Flow cl	Flow characteristic values (SI units)									
Dian	neter	Recommended flow	Factory settings							
[mm]	[inch]	Min./max. full scale value (v ~ 0.12/5 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 4 pulses/s)	Low flow (v ~ 0.02 m/s)					
50	2"	15 to 600 dm ³ /min	300 dm ³ /min	$1.25 dm^3$	2.25 dm ³ /min					
65	-	25 to 1000 dm ³ /min	500 dm ³ /min	2 dm ³	4 dm³/min					
80	3"	35 to 1500 dm ³ /min	750 dm ³ /min	3 dm ³	6 dm³/min					
100	4"	60 to 2400 dm ³ /min	1200 dm ³ /min	5 dm ³	9.5 dm ³ /min					
125	-	90 to 3700 dm ³ /min	1850 dm ³ /min	8 dm ³	15 dm ³ /min					
150	6"	145 to 5400 dm ³ /min	2500 dm ³ /min	10 dm ³	20 dm³/min					
200	8"	220 to 9400 dm ³ /min	5000 dm ³ /min	20 dm ³	35 dm³/min					
250	10"	20 to 850 m ³ /h	500 m ³ /h	0.03 m ³	3.5 m ³ /h					
300	12"	35 to 1300 m ³ /h	750 m ³ /h	0.05 m ³	5 m ³ /h					

Flow cl	Flow characteristic values (US units)									
Dian	neter	Recommended flow	Factory settings							
[inch]	[mm]	Min./max. full scale value current output $value (v \sim 0.12/5 \text{ m/s})$		Pulse value (~ 4 pulses/s)	Low flow (v ~ 0.02 m/s)					
2"	50	4 to 160 gal/min	75 gal/min	0.3 gal	0.7 gal/min					
-	65	7 to 260 gal/min	130 gal/min	0.5 gal	1.1 gal/min					
3"	80	10 to 400 gal/min	200 gal/min	0.8 gal	1.6 gal/min					
4"	100	16 to 650 gal/min	300 gal/min	1.2 gal	2.5 gal/min					
-	125	24 to 1000 gal/min	450 gal/min	1.8 gal	4 gal/min					
6"	150	40 to 1400 gal/min	600 gal/min	2.5 gal	6 gal/min					
8"	200	60 to 2500 gal/min	1200 gal/min	5 gal	10 gal/min					
10"	250	90 to 3700 gal/min	1500 gal/min	6 gal	16 gal/min					
12"	300	155 to 5700 gal/min	2400 gal/min	9 gal	23 gal/min					

Operable flow range

Over 1000 : 1

Output

Output signal Current output

- Galvanically isolated
- \bullet Active: 4 to 20 mA, $R_L < 700~\Omega$ (for HART: $R_L \ge 250~\Omega)$
- Full scale value adjustable
- Temperature coefficient: typ. 2 μ A/°C, resolution: 1.5 μ A

Pulse/status output

- Galvanically isolated
- Passive: 30 V DC / 250 mA
- Open collector
- Can be configured as:
 - Pulse output

Pulse value and pulse polarity can be selected, max. pulse width adjustable (5 to 2000 ms), pulse frequency max. 100 Hz

- Status output

For example, can be configured for error messages, empty pipe detection, flow recognition, limit value $\frac{1}{2}$

Signal on alarm

Current output

Failsafe mode can be selected (e.g. in accordance with NAMUR Recommendation NE 43)

Pulse output

Failsafe mode can be selected

Status output

"Not conductive" in the event of fault or power supply failure

Load

See "Output signal"

Low flow

Low flow cutoff, switch-on point can be selected as required

Galvanic isolation

All circuits for inputs, outputs and power supply are galvanically isolated from each other.

Power supply

Terminal assignment

Order information			Te	rminal No.			
"Input / Output"	24 (+)	25 (-)	26 (+)	27 (-)	1 (L1/L+)	2 (N/L-)	
A	Pulse/status output See "Outp		HART curr	ent output	Power supply See "Supply voltage"		
Functional values			out signal"				

Supply voltage

- 85 to 250 V AC, 45 to 65 Hz
- 20 to 28 V AC, 45 to 65 Hz, 11 to 40 V DC

Power consumption

Power consumption

- 85 to 250 V AC: < 12 VA (incl. sensor)
- 20 to 28 V AC: < 8 VA (incl. sensor)
- 11 to 40 V DC: < 6 W (incl. sensor)


Switch-on current

- Max. 16 A (< 5 ms) for 250 V AC
- Max. 5.5 A (< 5 ms) for 28 V AC
- Max. 3.3 A (< 5 ms) for 24 V DC

Power supply failure

Lasting min. ½ cycle frequency: EEPROM saves measuring system data


Electrical connection



Connecting the transmitter (aluminum field housing), cable cross-section max. 2.5 mm² (14 AWG)

- Electronics compartment cover
- Power supply cable
- Ground terminal for power supply cable
- d Terminal connector for power supply cable
- Electrode cable Ground terminal for electrode cable
- Terminal connector for electrode cable
- Service connector for connecting service interface FXA 193 (Fieldcheck, FieldCare)
- Ground terminal for potential equalization

Electrical connection, remote version



Connecting the remote version

- a Wall-mount housing connection compartment
- b Sensor connection housing cover
- c Electrode cable
- d Coil current cable
- n.c. Not connected, insulated cable shields

Cable colors/numbers for terminals:

5/6 = brown; 7/8 = white; 4 = green; 37/36 = yellow

Potential equalization



Note!

The measuring system must be included in the potential equalization.

Perfect measurement is only ensured when the fluid and the sensor have the same electrical potential. This is ensured by the reference electrode integrated in the sensor as standard.

The following should also be taken into consideration for potential equalization:

- Internal grounding concepts in the company
- Operating conditions, such as the material/grounding of the pipes (see table)

Standard situation

Operating conditions	Potential equalization
When using the measuring device in a: Metal, grounded pipe	
Potential equalization takes place via the ground terminal of the transmitter.	=
Note! When installing in metal pipes, we recommend you connect the ground terminal of the transmitter housing with the	
piping.	A0010831 Via the ground terminal of the transmitter

DN ≥ 350

Potential equalization

DN ≤ 300

flanges of the pipe

Special situations

Operating conditions

When using the measuring device in a:

• Metal pipe that is not grounded

This connection method also applies in situations where:

- Customary potential equalization cannot be ensured.
- Excessively high equalizing currents can be expected.

Both sensor flanges are connected to the pipe flange by means of a ground cable (copper wire, at least 6 $\,mm^2$ / $0.0093~in^2)$ and grounded. Connect the transmitter or sensor connection housing, as applicable, to ground potential by means of the ground terminal provided for the purpose.

Ground cable installation depends on the nominal diameter:

- DN ≤ 300 (12"): The ground cable is mounted directly on the conductive flange coating with the flange screws.
- DN \geq 350 (14"): The ground cable is mounted directly on the metal transport bracket.



The ground cable for flange-to-flange connections can be ordered separately as an accessory from Endress+Hauser.


When using the measuring device in a:

- Plastic pipe
- Pipe with insulating lining

This connection method also applies in situations where:

- $\, \blacksquare \,$ Customary potential equalization cannot be ensured.
- Excessively high equalizing currents can be expected.

Potential equalization takes place using additional ground disks, which are connected to the ground terminal via a ground cable (copper wire, at least 6 mm 2 / 0.0093 in 2). When installing the ground disks, please comply with the enclosed Installation Instructions.



Via the ground terminal of the transmitter and the

Via the ground terminal of the transmitter and the optionally available ground disks


When using the measuring device in a:

• Pipe with a cathodic protection unit

The device is installed potential-free in the pipe. Only the two flanges of the pipe are connected with a ground cable (copper wire, at least 6 $\rm mm^2$ / 0.0093 in²). Here, the ground cable is mounted directly on the conductive flange coating with flange screws.

Note the following when installing:

- The applicable regulations regarding potential-free installation must be observed.
- There should be **no** electrically conductive connection between the pipe and the device.
- The mounting material must withstand the applicable torques.



Potential equalization and cathodic protection

- Power supply isolation transformer
- Electrically isolated

Cable entry

Power supply and electrode cables (inputs/outputs):

- Cable entry M20 × 1.5 (8 to 12 mm / 0.31 to 0.47")
- Thread for cable entries, ½" NPT, G ½"

Connecting cable for remote version:

- Cable entry M20 × 1.5 (8 to 12 mm / 0.31 to 0.47")
- Thread for cable entries, ½" NPT, G ½"


Remote version cable specifications

Coil current cable

- $3 \times 0.75 \text{ mm}^2$ (18 AWG) PVC cable with common, braided copper shield ($\varnothing \sim 9 \text{ mm} / 0.35'$)
- Conductor resistance: $\leq 37 \Omega/\text{km} (\leq 0.011 \Omega/\text{ft})$
- Capacitance core/core, shield grounded: $\leq 120 \text{ pF/m}$ ($\leq 37 \text{ pF/ft}$)
- Operating temperature: -20 to +80 °C (-4 to +176 °F)
- Cable cross-section: max. 2.5 mm² (16 AWG)
- Test voltage for cable insulation: ≥ 1433 V AC r.m.s. 50/60 Hz or ≥ 2026 V DC

Electrode cable

- = 3×0.38 mm² (20 AWG) PVC cable with common, braided copper shield ($\varnothing \sim 9.5$ mm / 0.37") and individual shielded cores
- Conductor resistance: $\leq 50 \Omega/\text{km} (\leq 0.015 \Omega/\text{ft})$
- Capacitance core/shield: ≤ 420 pF/m (≤ 128 pF/ft)
- Operating temperature: -20 to +80 °C (-4 to +176 °F)
- Cable cross-section: max. 2.5 mm² (16 AWG)



A0003194

- a Electrode cable
- b Coil current cable
- 1 Core
- 2 Core insulation
- 3 Core shield
- 4 Core jacket 5 Core reinforcement
- Cahle shield
- 7 Outer jacket

Operation in zones of severe electrical interference

The measuring device complies with the general safety requirements in accordance with EN 61010-1, the EMC requirements of IEC/EN 61326 and NAMUR Recommendation NE 21.



Note!

Grounding is by means of the ground terminals provided for the purpose inside the connection housing.

Ensure that the stripped and twisted lengths of cable shield to the ground terminal are as short as possible.

Performance characteristics

Reference operating conditions

As per DIN EN 29104 and VDI/VDE 2641:

- Fluid temperature: +28 °C \pm 2 K (+82 °F \pm 2 K)
- Ambient temperature: $+22 \,^{\circ}\text{C} \pm 2 \,^{\circ}\text{K} (+72 \,^{\circ}\text{F} \pm 2 \,^{\circ}\text{K})$
- Warm-up period: 30 minutes


Installation conditions:

- Inlet run > 10 × DN
- Outlet run > 5 × DN
- Sensor and transmitter grounded.
- The sensor is centered in the pipe.

Maximum measured error

- Current output: also typically $\pm 5 \mu A$
- Pulse output: $\pm 0.5\%$ o.r. ± 2 mm/s ($\pm 0.5\%$ o.r. ± 0.08 in/s) (o.r. = of reading)

Fluctuations in the supply voltage do not have any effect within the specified range.



Max. measured error in % of reading

Repeatability

Max. $\pm 0.2\%$ o.r. ± 2 mm/s ($\pm 0.2\%$ o.r. ± 0.08 in/s) (o.r. = of reading)


Installations

Mounting location


Entrained air or gas bubble formation in the measuring tube can result in an increase in measuring errors.

Avoid the following installation locations in the pipe:

- Highest point of a pipeline. Risk of air accumulating!
- Directly upstream from a free pipe outlet in a vertical pipeline.



Mounting location




Installation of the sensor after a control valve is not recommended

1 Control valve

Installation of pumps

Pulsation dampers may be needed when using piston pumps, piston diaphragm pumps or hose pumps. Information on the shock and vibration resistance of the measuring system $\Rightarrow riangleq ri$



Installation of pumps

Partially filled pipes


Partially filled pipes with gradients necessitate a drain-type configuration.

The empty pipe detection function (EPD) provides additional security in detecting empty or partially filled pipes.



Note!


Risk of solids accumulating. Do not install the sensor at the lowest point in the drain. It is advisable to install a cleaning valve.



Installation with partially filled pipes

Down pipes

Install a siphon or a vent valve downstream of the sensor in down pipes $h \ge 5$ m (16.4 ft). This precaution is to avoid low pressure and the consequent risk of damage to the lining of the measuring tube. This measure also prevents the liquid current stopping in the pipe which could cause air locks. Information on the pressure tightness of the measuring tube lining $\Rightarrow \textcircled{1}{2}$ 21, Section "Pressure tightness".



Installation measures for vertical pipes


- 1 Vent valve
- Pipe siphon
- h Length of the down pipe

Orientation

An optimum orientation helps avoid gas and air accumulations and deposits in the measuring tube. However, the measuring device also offers the additional function of empty pipe detection (EPD) for detecting partially filled measuring tubes or if outgassing fluids or fluctuating operating pressures are present.

Vertical orientation

This is the ideal orientation for self-emptying piping systems and for use in conjunction with empty pipe detection.



Vertical orientation

14 Endress+Hauser


A00081

Horizontal orientation

The measuring electrode axis should be horizontal. This prevents brief insulation of the two measuring electrodes by entrained air bubbles.



Empty pipe detection only works correctly with horizontal orientation if the transmitter housing is facing upwards. Otherwise there is no guarantee that empty pipe detection will respond if the measuring tube is only partially filled or empty.



Horizontal orientation


- 2 3
- EPD electrode for empty pipe detection Measuring electrodes for signal detection Reference electrode for potential equalization

Inlet and outlet run


If possible, install the sensor well clear of assemblies such as valves, T-pieces, elbows etc.

Note the following inlet and outlet runs to comply with measuring accuracy specifications:

- Inlet run: \geq 5 × DN
- Outlet run: $\geq 2 \times DN$



Inlet and outlet run standard version



Optional version: w/o inlet and outlet run

Adapters


Suitable adapters to DIN EN 545 (double-flange reducers) can be used to install the sensor in larger-diameter pipes. The resultant increase in the rate of flow improves measuring accuracy with very slow-moving fluids. The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders.



Note!

The nomogram only applies to liquids of viscosity similar to water.

- 1. Calculate the ratio of the diameters d/D.
- 2. From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.




Pressure loss due to adapters

Length of connecting cable

When mounting the remote version, please note the following to achieve correct measuring results:

- Fix cable run or lay in armored conduit. Cable movements can falsify the measuring signal especially in the case of low fluid conductivities.
- Route the cable well clear of electrical machines and switching elements.
- If necessary, ensure potential equalization between sensor and transmitter.
- The permitted cable length L_{max} is determined by the fluid conductivity. A minimum conductivity of 50 μ S/cm is needed for all fluids.
- When the empty pipe detection function is switched on (EPD), the maximum connecting cable length is 10 m (33 ft).



Permitted length of connecting cable for remote version Area marked in gray = permitted range; L_{max} = length of connecting cable in [m] ([ft]); fluid conductivity in $[\mu S/cm]$

Environment

Ambient temperature range

Transmitter

■ -20 to +60 °C (-4 to +140 °F)

Sensor

- Flange material carbon steel: -10 to +60 °C (+14 to +140 °F)
- Flange material stainless steel: -40 to +60 °C (-40 to +140 °F)



Note!

The permitted temperature range of the measuring tube lining may not be undershot or overshot (\rightarrow 18, Section "Medium temperature range").

Please note the following points:

- Install the device in a shady location. Avoid direct sunlight, particularly in warm climatic regions.
- The transmitter must be mounted separate from the sensor if both the ambient and fluid temperatures are high.

Storage temperature

The storage temperature corresponds to the operating temperature range of the measuring transmitter and the appropriate measuring sensors.



Notel

- The measuring device must be protected against direct sunlight during storage in order to avoid unacceptably high surface temperatures.
- A storage location must be selected where moisture does not collect in the measuring device. This will help prevent fungus and bacteria infestation which can damage the liner.

Degree of protection

- Standard: IP 67 (NEMA 4X) for transmitter and sensor.
- Optional: IP 68 (NEMA 6P) for sensor for remote version.
- For information regarding applications where the device is buried directly in the soil or is installed in a flooded wastewater basin please contact your local Endress+Hauser Sales Center.

Shock and vibration resistance

Acceleration up to 2 g following IEC 600 68-2-6

Electromagnetic compatibility (EMC)

- As per IEC/EN 61326 as well as NAMUR Recommendation NE 21
- Emission: to limit value for industry EN 55011

Process

Medium temperature range

The permitted temperature depends on the measuring tube lining:

- Polyurethane: -20 to +50 °C (-4 to +122 °F) (DN 25 to 1200 / 1 to 48")
- Hard rubber: 0 to +80 °C (+32 to +176 °F) (DN 50 to 2000 / 2 to 78")

Conductivity

The minimum conductivity is: $\geq 50 \,\mu\text{S/cm}$



In the remote version, the necessary minimum conductivity also depends on the cable length


Pressure-temperature ratings

Caution!

The following diagrams contain material load diagrams (reference curves) for flange materials with regard to the medium temperature. However, the maximum medium temperatures permitted always depend on the lining material of the sensor and/or the sealing material.

Flange connection to EN 1092-1 (DIN 2501)


Material: S235JRG2, S235JR+N, P250GH, P245GH, E250C, A105



A0021188-FN

Flange connection to EN 1092-1 (DIN 2501)


Material: 1.4571, 1.4404, F316L



A0021184-EN


Flange connection to ASME B16.5

Material: A 105




Flange connection to ASME B16.5

Material: F316L




Flange connection to AWWA C207, Class D

Material: A105, A181 Cl.70, P265GH, S275JR, E250C, S235JRG2




Flange connection to JIS B2220 $\,$

Material: A105, A350 LF2, F316L




Flange connection to AS 2129 Table E

Material: A105, P235GH, P265GH, S235JRG2



Flange connection to AS 4087 PN 16

Material: A105, P265GH, S275JR



Medium pressure range (nominal pressure)

- EN 1092-1 (DIN 2501)
 - PN 6 (DN 350 to 2000 / 14 to 78")
 - PN 10 (DN 200 to 2000 / 8 to 78")
 - PN 16 (DN 65 to 2000 / 3 to 78")
 - PN 25 (DN 200 to 1000 / 8 to 40")
 - PN 40 (DN 25 to 150 / 1 to 6")
- ASME B 16.5
 - Class 150 (DN 25 to 600 / 1 to 24")
 - Class 300 (DN 25 to 150 / 1 to 6")
- AWWA C2072
 - Class D (DN 700 to 2000 / 28 to 78")
- JIS B2220
 - 10 K (DN 50 to 750 / 2 to 30")
 - 20 K (DN 25 to 600 / 1 to 24")
- AS 2129
 - Table E (DN 80, 100, 150 to 1200 / 3", 4", 6 to 48")
- AS 4087
 - PN 16 (DN 80, 100, 150 to 1200 / 3", 4", 6 to 48")

Pressure tightness

Measuring tube lining: Polyurethane

Nominal diameter		Limit values for abs. pressure [mbar] ([psi]) at fluid temperatures:				
		25 °C (77 °F)		50 °C (122 °F)		
[mm] [inch]		[mbar] [psi]		[mbar]	[psi]	
25 to 1200	1 to 48"	0	0	0	0	

Measuring tube lining: Hard rubber

Nominal	diameter	Limit values	for abs. pres	ssure [mbar]	([psi]) at flu	id temperatu	ıres:
		25 °C (77 °F) 70 °C (158 °F)			80 °C (80 °C (176 °F)	
[mm]	[inch]	[mbar]	ar] [psi] [mbar] [psi]		[mbar]	[psi]	
50 to 2000	2 to 78"	0	0	0 0 0			

Limiting flow

The diameter of the pipe and the flow rate determine the nominal diameter of the sensor. The optimum flow velocity is between 2 to 3 m/s (6.5 to 9.8 ft/s).

The velocity of flow (v), moreover, has to be matched to the physical properties of the fluid:

- v < 2 m/s (6.5 ft/s): for abrasive fluids such as potter's clay, lime milk, ore slurry etc.
- v > 2 m/s (6.5 ft/s): for fluids causing build-up such as wastewater sludges etc.




Note!

- For fluids with high levels of solids, the selection of a pipe with nominal diameter > DN 8 (3/8") may be considered, to improve the stability of the signal and cleanability due to larger electrodes.


Pressure loss

- $\ \ \, \blacksquare$ No pressure loss if the sensor is installed in a pipe with the same nominal diameter.
- Pressure losses for configurations incorporating adapters according to DIN EN 545
 (→

 16, Section "Adapters").



Pressure loss DN 50 to 80 (2 to 3") for optional version w/o inlet and outlet runs




Pressure loss DN 100 to 300 (4 to 12") for optional version w/o inlet and outlet runs

Vibrations

Secure the piping and the sensor if vibration is severe.



Note!




Measures to prevent vibration of the measuring device

L > 10 m (33 ft)

Mechanical construction

Design, dimensions

Transmitter, remote version



Transmitter dimensions, remote version

Dimensions in SI units


	А	В	С	D	E	F	G	ØН
	178	113	135	20 to 27.5	153 to 168	113	100	8.6 (M8)
	J	K	L	M	N	0	Р	
İ	123	150	100	25	133	177.5	327.5	

All dimensions in [mm]

Dimensions in US units

	А	В	С	D	E	F	G	ØН
ĺ	7.00	4.45	5.31	0.79 to 1.08	6.02 to 6.61	4.45	3.94	0.34 (M8)
İ	J	K	L	M	N	0	Р	
	4.84	5.90	3.94	0.98	5.24	6.99	12.89	


All dimensions in [inch]



Transmitter mounting, remote version. Engineering unit mm (in)

- A Direct wall mounting
- B Pipe mounting

Compact version DN \leq 300 (12")



Standard version

Dimensions in SI units

DN	L 1)	А	В	С	D	Е	F	G	Н	J	K
EN (DIN) / JIS / AS ²⁾											
25	200						341	257	84	94	120
32	200						341	257	84	94	120
40	200						341	257	84	94	120
50	200					150	341	257	84	94	120
65	200						391	282	109	94	180
80	200	178	20 to 27.5	153 to 168	113		391	282	109	94	180
100	250	1/0	20 10 27.5	155 (0 100	115		391	282	109	94	180
125	250						472	322	150	140	260
150	300						472	322	150	140	260
200	350						527	347	180	156	324
250	450	1					577	372	205	166	400
300	500	1					627	397	230	166	460

Dimensions in US units

DN	L 1)	А	В	С	D	Е	F	G	Н	J	K
ASME											
1"	7.87						13.4	10.1	3.31	3.70	4.72
1½"	7.87						13.4	10.1	3.31	3.70	4.72
2"	7.87						13.4	10.1	3.31	3.70	4.72
3"	7.87						15.4	11.1	4.29	3.70	7.09
4"	9.84	7.01	0.79 to 1.08	6.02 to 6.61	4.45	5.91	15.4	11.1	4.29	3.70	7.09
6"	11.8						18.6	12.7	5.91	5.51	10.2
8"	13.8						20.8	13.7	7.09	6.14	12.8
10"	17.7						22.7	14.7	8.07	6.14	15.8
12"	19.7						24.7	15.6	9.06	6.54	18.1

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW. All dimensions in [inch]

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
2) For flanges to AS, only the nominal diameters DN 80, 100 and 150 to 300 are available. All dimensions in [mm]

Optional version w/o inlet and outlet runs

Dimensions in SI units

DN	L 1)	А	В	С	D	Е	F	G	Н	J	K
EN (DIN) / JIS / AS ²⁾											
50	200						341	257	84	94	120
65	200						341	257	84	94	120
80	200						391	282	109	94	180
100	250						391	282	109	94	180
125	250	178	20 to 27.5	153 to 168	113	150	391	282	109	94	180
150	300						391	282	109	94	180
200	350						472	322	150	140	260
250	450						472	322	150	140	260
300	500						527	347	180	156	324


Dimensions in US units

DN	L 1)	А	В	С	D	Е	F	G	Н	J	K
ASME											
2"	7.87						13.4	10.1	3.31	3.70	4.72
3"	7.87						15.4	11.1	4.29	3.70	7.09
4"	9.84						15.4	11.1	4.29	3.70	7.09
6"	11.8	7.01	0.79 to 1.08	6.02 to 6.61	4.45	5.91	15.4	11.1	4.29	3.70	7.09
8"	13.8						18.6	12.7	5.91	5.51	10.2
10"	17.7						18.6	12.7	5.91	5.51	10.2
12"	19.7						20.8	13.7	7.09	6.14	12.8

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW. All dimensions in [inch]

 $^{^{1)}}$ The length is regardless of the pressure rating selected. Fitting length to DVGW. $^{2)}$ For flanges to AS, only the nominal diameters DN 80, 100 and 150 to 300 are available. All dimensions in [mm]

Compact version DN \geq 350 (14")



Dimensions in SI units

DN	L 1)	А	В	С	D	Е	F	G	Н	J	K
EN (DIN) / AS 2)											
350	550						738.5	456.5	282.0	288	564
375	600						790.5	482.5	308.0	288	616
400	600						790.5	482.5	308.0	288	616
450	650						840.5	507.5	333.0	292	666
500	650						891.5	533.0	358.5	292	717
600	780						995.5	585.0	410.5	402	821
700	910						1198.5	686.5	512.0	589	1024
750	975						1198.5	686.5	512.0	626	1024
800	1040						1241.5	708.5	533.5	647	1067
900	1170	178	20 to 27.5	153 to 168	113	150	1394.5	784.5	610.0	785	1220
1000	1300	1/0	20 (0 27.5	155 (0 100		150	1546.5	860.5	686.0	862	1372
1050	1365						1598.5	886.5	712.0	912	1424
1200	1560						1796.5	985.5	811.0	992	1622
1350	1755						1998.5	1086.5	912.0	1252	1824
1400	1820						2148.5	1161.5	987.0	1252	1974
1500	1950						2196.5	1185.5	1011.0	1392	2022
1600	2080						2286.5	1230.5	1056.0	1482	2112
1650	2145						2360.5	1267.5	1093.0	1482	2186
1800	2340						2550.5	1362.5	1188.0	1632	2376
2000	2600						2650.5	1412.5	1238.0	1732	2476


¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
2) For flanges to AS, only DN 350, 400, 500 and 600 are available.
All dimensions in [mm]

Dimensions in US units

DN ASME / AWWA	L 1)	A	В	С	D	Е	F	G	Н	J	K
14"	21.6						29.1	17.9	11.1	11.3	22.2
15"	23.6						31.1	18.9	12.1	11.3	24.2
16"	23.6						31.1	18.9	12.1	11.3	24.2
18"	25.6						33.1	19.9	13.1	11.5	26.2
20"	25.6						35.1	20.9	14.1	11.5	28.2
24"	30.7						39.2	23.0	16.2	15.8	32.3
28"	35.8						47.2	27.0	20.1	23.2	40.3
30"	38.4						47.2	27.0	20.1	24.6	40.3
32"	40.9						48.9	27.9	21.0	25.5	42.0
36"	46.0	7.01	0.79 to 1.08	6.02 to 6.61	4.45	5.91	54.9	30.9	24.0	30.9	48.0
40"	51.2	7.01	0.79 to 1.00	0.02 to 0.01	4.45	2.91	60.9	33.9	27.0	33.9	54.0
42"	53.7						62.9	34.9	28.0	35.9	56.0
48"	61.4						71.7	38.8	31.9	39.0	63.8
54"	69.1						78.7	42.8	35.9	42.3	71.8
56"	71.7						84.6	45.7	38.9	49.3	77.7
60"	76.8						86.5	46.7	39.8	54.8	79.6
64"	81.9						90.0	48.4	41.6	58.4	83.2
66"	84.4						92.9	49.9	43.0	58.4	86.0
72"	92.1						100.4	53.6	46.8	64.2	93.5
78"	102.3						104.3	55.6	48.7	68.2	97.5

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW. 2) Flanges \leq DN 600 only to ASME available, \geq DN 700 only to AWWA available. All dimensions in [inch]

Sensor, remote version DN \leq 300 (12")



Standard version

Dimensions in SI units

DN	L 1)	А	В	С	D	Е	F	G	Н	J
EN (DIN) / JIS / AS ²⁾										
25	200	129	163	143	102	286	202	84	120	94
32	200	129	163	143	102	286	202	84	120	94
40	200	129	163	143	102	286	202	84	120	94
50	200	129	163	143	102	286	202	84	120	94
65	200	129	163	143	102	336	227	109	180	94
80	200	129	163	143	102	336	227	109	180	94
100	250	129	163	143	102	336	227	109	180	94
125	250	129	163	143	102	417	267	150	260	140
150	300	129	163	143	102	417	267	150	260	140
200	350	129	163	143	102	472	292	180	324	156
250	450	129	163	143	102	522	317	205	400	166
300	500	129	163	143	102	572	342	230	460	166

Dimensions in US units

DN	L 1)	А	В	С	D	Е	F	G	Н	J
ASME										
1"	7.87					11.3	7.95	3.32	4.72	3.70
1½"	7.87					11.3	7.95	3.32	4.72	3.70
2"	7.87					11.3	7.95	3.32	4.72	3.70
3"	7.87					13.2	8.94	4.30	7.10	3.70
4"	9.84	5.08	6.42	5.63	4.02	13.2	8.94	4.30	7.10	3.70
6"	11.8					16.4	10.5	5.91	10.2	5.51
8"	13.8					18.6	11.5	7.10	12.8	6.14
10"	17.7					20.6	12.5	8.08	15.8	6.14
12"	19.7					22.5	13.5	9.06	18.1	6.54

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW. All dimensions in [inch]

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
2) For flanges to AS, only the nominal diameters DN 80, 100 and 150 to 300 are available. All dimensions in [mm]

Optional version w/o inlet and outlet runs

Dimensions in SI units

DN	L 1)	А	В	С	D	E	F	G	Н	J
EN (DIN) / JIS / AS 2)										
50	200					286	202	84	120	94
65	200					286	202	84	120	94
80	200				•	336	227	109	180	94
100	250					336	227	109	180	94
125	250	129	163	143	102	336	227	109	180	94
150	300				•	336	227	109	180	94
200	350				•	417	267	150	260	140
250	450				•	417	267	150	260	140
300	500				•	472	292	180	324	156


Dimensions in US units

DN	L 1)	А	В	С	D	Е	F	G	Н	J
ASME										
2"	7.87					11.3	7.95	3.32	4.72	3.70
3"	7.87					13.2	8.94	4.30	7.10	3.70
4"	9.84					13.2	8.94	4.30	7.10	3.70
6"	11.8	5.08	6.42	5.63	4.02	13.2	8.94	4.30	7.10	3.70
8"	13.8					16.4	10.5	5.91	10.2	5.51
10"	17.7					16.4	10.5	5.91	10.2	5.51
12"	19.7					18.6	11.5	7.10	12.8	6.14

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW. All dimensions in [inch]

¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
2) For flanges to AS, only the nominal diameters DN 80, 100 and 150 to 300 are available. All dimensions in [mm]

Sensor, remote version DN ≥ 350 (14")



Dimensions in SI units

DN EN (DIN) / AS ²⁾	L 1)	А	В	С	D	Е	F	G	Н	J
350	550					683.5	401.5	282.0	564	288
375	600					735.5	427.5	308.0	616	288
400	600					735.5	427.5	308.0	616	288
450	650					785.5	452.5	333.0	666	292
500	650					836.5	478.0	358.5	717	292
600	780					940.5	530.0	410.5	821	402
700	910					1143.5	631.5	512.0	1024	589
750	975					1143.5	631.5	512.0	1024	626
800	1040					1186.5	653.0	533.5	1067	647
900	1170	129	163	143	102	1339.5	729.5	610.0	1220	785
1000	1300	129	105	145	102	1491.5	805.5	686.0	1372	862
1050	1365					1543.5	831.5	712.0	1424	912
1200	1560					1741.5	930.5	811.0	1622	992
1350	1755					1943.5	1031.5	912.0	1824	1252
1400	1820					2093.5	1106.5	987.0	1974	1252
1500	1950				-	2141.5	1130.5	1011.0	2022	1392
1600	2080					2231.5	1175.5	1056.0	2112	1482
1650	2145					2305.5	1212.5	1093.0	2186	1482
1800	2340					2495.5	1307.5	1188.0	2376	1632
2000	2600					2595.5	1357.5	1238.0	2476	1732


¹⁾ The length is regardless of the pressure rating selected. Fitting length to DVGW.
2) For flanges to AS, only DN 350, 400, 500 and 600 are available.
All dimensions in [mm]

Dimensions in US units

DN ASME / AWWA ²⁾	L 1)	A	В	С	D	Е	F	G	Н	J
14"	21.6					29.1	15.8	11.1	22.2	11.3
15"	23.6					31.1	16.8	12.1	24.2	11.3
16"	23.6					31.1	16.8	12.1	24.2	11.3
18"	25.6					33.1	17.8	13.1	26.2	11.5
20"	25.6					35.1	18.8	14.1	28.2	11.5
24"	30.7					39.2	20.9	16.2	32.3	15.8
28"	35.8					45.0	24.9	20.1	40.3	23.2
30"	38.4					45.0	24.9	20.1	40.3	24.6
32"	40.9					46.7	25.7	21.0	42.0	25.5
36"	46.0	5.08	6.42	5.63	4.02	52.7	28.7	24.0	48.0	30.9
40"	51.2	5.00	0.42	5.05	4.02	58.7	31.7	27.0	54.0	33.9
42"	53.7					60.7	32.7	28.0	56.0	35.9
48"	61.4					68.5	36.6	31.9	63.8	39.0
54"	69.1					76.5	40.6	35.9	71.8	42.3
56"	71.7					82.4	43.6	38.9	77.7	49.3
60"	76.8					84.3	44.5	39.8	79.6	54.8
64"	81.9					87.9	46.3	41.6	83.2	58.4
66"	84.4					90.8	47.7	43.0	86.0	58.4
72"	92.1					98.2	51.5	46.8	93.5	64.2
78"	102.3					102.2	53.4	48.7	97.5	68.2

 $^{^{1)}}$ The length is regardless of the pressure rating selected. Fitting length to DVGW. $^{2)}$ Flanges \leq DN 600 only to ASME available, \geq DN 700 only to AWWA available. All dimensions in [inch]

Ground disk for flange connections



Dimensions (SI units)

DN ¹⁾ EN (DIN) / JIS / AS ²⁾	A	В	С	D	E	t
25	26	62	77.5	87.5		
32	35	80	87.5	94.5		
40	41	82	101	103		
50	52	101	115.5	108		
65	68	121	131.5	118		
80	80	131	154.5	135		
100	104	156	186.5	153	6.5	
125	130	187	206.5	160		
150	158	217	256	184		
200	206	267	288	205		2
250	260	328	359	240		
300 ³⁾	312	375	413	273		
300 ⁴⁾	310	375	404	268		
350 ³⁾	343	433	479	365		
375 ³⁾	393	480	542	395		
400 3)	393	480	542	395	9.0	
450 ³⁾	439	538	583	417	7.0	
500 ³⁾	493	592	650	460		
600 ³⁾	593	693	766	522		

¹⁾ Ground disks can be used for all flange standards/pressure ratings that can be delivered, except for DN \geq 300.
2) Only DN 32, 40, 65 and 125 are available for flanges according to AS.
3) PN 10/16
4) PN 25, JIS 10K/20K

All dimensions in [mm]

Dimensions (US units)

DN ¹⁾	А	В	С	D	Е	t
ASME						
1"	1.02	2.44	3.05	3.44		
11/2"	1.61	3.23	3.98	4.06		
2"	2.05	3.98	4.55	4.25		
3"	3.15	5.16	6.08	5.31		
4"	4.09	6.14	7.34	6.02	0.26	0.08
6"	6.22	8.54	10.08	7.24		
8"	8.11	10.5	11.3	8.07		
10"	10.2	12.9	14.1	9.45		
12"	12.3	14.8	16.3	10.8		
14"	13.5	17.1	18.9	14.4		
15"	15.45	18.9	21.3	15.6		
16"	15.45	18.9	21.3	15.6	0.35	
18"	17.3	21.2	23.0	16.4	0.55	
20"	19.4	23.3	25.6	18.1		
24"	23.4	27.3	30.1	20.6		

¹⁾ Ground disks can be used for all flange standards/pressure ratings.
All dimensions in [inch]

Weight

Standard version

Weight in SI units

Weight	ght data in kg													
Diamet	er		С	omp	act version	on		Remote version (without cable)						
								Sensor						Transmitter
[mm]	[inch]	EN	(DIN) / AS ¹⁾		JIS ASME / AWWA		EN	EN (DIN) / JIS AS ¹⁾			ASME / AWWA		Wall housing	
25	1"		5.7		5.7		5.7		5.3		5.3		5.3	
32	-	40	6.4	-	5.7		-	PN 40	6.0		5.3		-	
40	11/2"	PN	7.8		6.7		7.8		7.4		6.3		7.4	
50	2"		9.0		7.7		9.0		8.6		7.3		8.6	
65	-		10.4		9.5		-		10.0		9.1		-	
80	3"	2	12.4		10.9		12.4	.0	12.0		10.5		12.0	
100	4"	PN 16	14.4		13.1		14.4	PN 16	14.0		12.7		14.0	
125	-	Ъ	19.9		19.4		_	Ъ	19.5		19.0		-	
150	6"		23.9		22.9	150	23.9		23.5		22.5	150	23.5	
200	8"	0	43.4		40.3	Class	43.3	0	43		39.9	Class	43	
250	10"	PN 10	63.4		67.8	O	73.4	PN 10	63		67.4 70.3	Ü	73	
300	12"	Ъ	68.4		70.7		108.4		68				108	
350	14"		105		81.1		175		103		79.1		173	
375	15"		120		-	205 11	118		-		-			
400	16"		120		102		205	-	118		100		203	
450	18"		161		130		255		159		128		253	
500	20"		156	10K	144		285		154	10K	142		283	3.1
600	24"		208		190		405		206		188		403	
700	28"		304		282		400		302		280		398	
-	30"		-		333		460		-		331		458	
800	32"		357		-		550		355		-		548	
900	36"		485		-		800	_	483		-		798	
1000	40"	PN 6	589		-		900	PN 6	587		-		898	
-	42"	1	-		-		1100	T.	-		-		1098	
1200	48"		850		-	D	1400		848		-	D	1398	
-	54"		-		-	Class	2200		-		-	Class	2198	
1400	-		1300		-	O	-		1298		-	O	-	
-	60"		-		-		2700		-		-		2698	
1600	-		1700		-		-		1698		-		-	
_	66"		_		-		3700		-		-		3698	
1800	72"		2200		-		4100		2198	-	-		4098	
-	78"		-		-		4600		-		-		4598	
2000	-		2800		-		-		2798		-		-	

¹⁾ For flanges to AS, only DN 80, 100, 150 to 400, 500 and 600 are available.

Transmitter (compact version): 1.8 kg
 Weight data valid for standard pressure ratings and without packaging material

Weight in US units (only ASME/AWWA)

Weight data	a in lbs					
Diameter		Compact version			Remote version (v	vithout cable)
			Sensor			Transmitter
[mm]	[inch]		ASME /AWWA		ASME / AWWA	Wall housing
25	1"		12.6		11.7	
40	1½"		17.2		16.3	
50	2"		19.9		19.0	
80	3"		27.3		26.5	
100	4"		31.8		30.9	
150	6"		52.7	Class 150	51.8	
200	8"	150	95.5		94.8	
250	10"	Class	162.1		161.0	
300	12"	C	239.0		238.1	
350	14"		380.1		381.5	
400	16"		448.5		447.6	
450	18"		558.8		557.9	
500	20"		624.9		624.0	6.8
600	24"		889.5		888.6	0.0
700	28"		878.5		877.6	
-	30"		1010.8		1009.9	
800	32"		1209.2		1208.3	
900	36"		1760.5		1759.6	
1000	40"		1981.0		1980.1	
_	42"	s D	2422.0	s D	2421.1	
1200	48"	Class D	3083.5	Class D	3082.6	
-	54"		4847.5		4846.6	
-	60"		5950.0		5949.1	
-	66"		8155.0		8154.1	
1800	72"		9037.0		9036.1	
-	78"		10139.0		10139.0	

Transmitter (compact version): 4.0 lbs
 Weight data valid for standard pressure ratings and without packaging material

Optional version w/o inlet and outlet runs

Weight in SI units

Weight	Weight data in kg													
Diamet	er	Compact version						Remote version (without cable)					able)	
										5	Sensor			Transmitter
[mm]	[inch]		(DIN) / AS ¹⁾	, ,			ASME / EN		(DIN) / AS ¹⁾	JIS		ASME / AWWA		Wall housing
50	2"	PN 40	9.6		8.3		9.6	PN 40	9.2		7.9		9.2	6.8
65	-		11.4		10.5		-		11.0		10.1		-	
80	3"	9	13.8		12.3		13.8	13.4		11.9	13.4			
100	4"	PN 1	15.4	OK	14.9	150	16.5	PN 1	15.0	10K	14.5	150	16.1	
125	-	Ъ	23.9	1(23.8	Class	-	Ъ	23.5	1(23.4	Class	-	
150	6"		29.2		29.9	O	30.9		28.8		29.5	0	30.5	
200	8"	0	51.7		49.5		52.9	0	51.3		49.1		52.6	
250	10"	PN 10	80.5		82.7		90.6	PN 10	80.1		82.3		90.2	
300	12"	Ь	94.1		88.9		129.8	Ь	93.7		88.5		129.4	

¹⁾ For flanges to AS, only DN 80, 100, 150 to 400, 500 and 600 are available.

- Transmitter (compact version): 1.8 kg
 Weight data valid for standard pressure ratings and without packaging material

Weight in US units (only ASME/AWWA)

Weight data	Weight data in lbs							
Diameter		Compact version			Remote version (without cable)			
					Sensor	Transmitter		
[mm]	[inch]		ASME /AWWA		ASME / AWWA	Wall housing		
50	2"		21.2		20.3			
80	3"		30.4		29.6			
100	4"	50	36.4	20	35.5			
150	6"	ss 1	68.1	ss 1	67.2	6.8		
200	8"	Cla	116.7	Cla	116.0			
250	10"		200.0		198.9			
300	12"		286.2		285.3			

- Transmitter (compact version): 4.0 lbs
 Weight data valid for standard pressure ratings and without packaging material

Measuring tube specifications

Dian	neter			Pressur	e rating			I	nternal	diamete	r
		EN (DIN)	AS 2129	AS 4087	ASME	AWWA	JIS		ubber	Polyur	
[mm]	[inch]	[bar]			[lbs]		J-2	[mm]	[inch]	[mm]	[inch]
25	1"	PN 40	_	_	Cl. 150	_	20 K	-	_	24	0.94
32	-	PN 40	-	_	-	_	20 K	-	-	32	1.26
40	1½"	PN 40	_	_	Cl. 150	_	20 K	_	-	38	1.50
50	2"	PN 40	Table E	PN 16	Cl. 150	_	10 K	50	1.97	50	1.97
65	-	PN 16	-	_	-	_	10 K	66	2.60	66	2.60
80	3"	PN 16	Table E	PN 16	Cl. 150	-	10 K	79	3.11	79	3.11
100	4"	PN 16	Table E	PN 16	Cl. 150	-	10 K	102	4.02	102	4.02
125	-	PN 16	-	-	_	-	10 K	127	5.00	127	5.00
150	6"	PN 16	Table E	PN 16	Cl. 150	-	10 K	156	6.14	156	6.14
2001)	8"	PN 10	Table E	PN 16	Cl. 150	-	10 K	204	8.03	204	8.03
2002)	8"	PN 16	Table E	PN 16	Cl. 150	-	10 K	201	7.91	-	-
2501)	10"	PN 10	Table E	PN 16	Cl. 150	_	10 K	258	10.2	258	10.2
2502)	10"	PN 16	Table E	PN 16	Cl. 150	_	10 K	251	9.88	1	-
3001)	12"	PN 10	Table E	PN 16	Cl. 150	_	10 K	309	12.2	309	12.2
3002)	12"	PN 16	Table E	PN 16	Cl. 150	_	10 K	309	12.2	1	-
350	14"	PN 6	Table E	PN 16	Cl. 150	_	10 K	342	13.5	342	13.5
375	15"	-	-	PN 16	ı	_	-	392	15.4	ı	-
400	16"	PN 6	Table E	PN 16	Cl. 150	_	10 K	392	15.4	392	15.4
450	18"	PN 6	_	-	Cl. 150	-	10 K	437	17.2	437	17.2
500	20"	PN 6	Table E	PN 16	Cl. 150	_	10 K	492	19.4	492	19.4
600	24"	PN 6	Table E	PN 16	Cl. 150	-	10 K	594	23.4	594	23.4
700	28"	PN 6	-	-	ı	Class D	10 K	692	27.2	692	27.2
750	30"	_	_	-	1	Class D	10 K	742	29.2	742	29.2
800	32"	PN 6	_	_	1	Class D	-	794	31.3	794	31.3
900	36"	PN 6	-	-	ı	Class D	-	891	35.1	891	35.1
1000	40"	PN 6	-	-	ı	Class D	-	994	39.1	994	39.1
-	42"	-	_	_	-	Class D	-	1043	41.1	1043	41.1
1200	48"	PN 6	-	-	-	Class D	-	1197	47.1	1197	47.1
-	54"		-	-	-	Class D	-	1339	52.7	-	-
1400	-	PN 6	-	-	1	-	-	1402	55.2	ı	1
-	60"	-	-	_	-	Class D	-	1492	58.7	-	-
1600	-	PN 6	_	-	1	-	-	1600	63.0	-	-
-	66"	-	-	-	1	Class D	-	1638	64.5	ı	1
1800	72"	PN 6	-	_	-	Class D	-	1786	70.3	-	-
2000	78"	PN 6	-	-	-	Class D	-	1989	78.3	-	-

¹⁾ Standard version

²⁾ Optional version w/o inlet and outlet runs

Material

- Housing: powder-coated die-cast aluminum
- Sensor housing
 - DN 25 to 300 (1 to 12"): powder-coated die-cast aluminum
 - DN 350 to 2000 (14 to 78"): with protective lacquering
- Measuring tube
 - DN ≤ 300 (12"): stainless steel 1.4301 (304) or 1.4306 (304L);
 (Flange material: carbon steel with Al/Zn protective coating)
 - DN ≥ 350 (14"): stainless steel 1.4301 (304) or 1.4306 (304L);
 (Flange material: carbon steel with protective lacquering)
- Electrodes: 1.4435 (316L), Alloy C22
- Flange
 - EN 1092-1 (DIN2501)
 - DN 25 to 3501:
 - Stainless-steel, 1.4571, F316L
 - Carbon steel, S235JRG2, S235JR+N, P250GH, P245GH, E250C, A105
 - DN 350 to 6001:
 - Stainless-steel, 1.4571, F316
 - Carbon steel, P245GH, S235JRG2, S235JR+N, A105, E250C
 - DN > 6001:
 - Stainless-steel, 1.4404, F316L
 - Carbon steel, P245GH, S235JRG2, S235JR+N, P250GH, E250C
 - ASME B16.5
 - DN 25 to 600
 - Stainless-steel, F316L similar to 1.4404
 - Carbon steel, A105
 - AWWA C207: Carbon steel, A105, Cl.70 A181, P265GH, S275JR, E250C
 - JIS B2220:
 - Carbon steel, A105, A350 LF2
 - Stainless steel, F316L

(DN \leq 300 (12") with Al/Zn protective coating; DN \geq 350 (14") with protective lacquering)

- AS 2129: Carbon steel, A105, P235GH, P265GH, S235JRG2
- AS 4087: Carbon steel, A105, P265GH, S275JR
- Seals: to DIN EN 1514-1 IBC form
- Ground disks: 1.4435 (316L) or Alloy C22

10rder code "Design", option A "insertion length short"

Fitted electrodes

Measuring electrodes, reference electrodes and empty pipe detection electrodes available as standard with:

- 1.4435 (316L)
- Alloy C22

Process connections

Flange connection:

- EN 1092-1 (DIN 2501), DN \leq 300 (12") form A, DN \geq 350 (14") form B (Dimensions to DIN 2501, DN 65 PN 16 and DN 600 (24") PN 16 exclusively to EN 10921)
- ASME B16.5
- AWWA C 207, Class D
- JIS B2220
- AS 2129 Table E
- AS 4087 PN 16

Surface roughness

Electrodes with 1.4435 (316L), Alloy C22: \leq 0.3 to 0.5 μm (12 to 20 μin) (All data refer to parts in contact with medium)

Operability

Local operation

Display elements

• Liquid crystal display: unilluminated, two-line, 16 characters per line

- Display (operating mode) preconfigured: volume flow and totalizer status
- 1 totalizer

Operating elements

Local operation via three keys (S, O, F)

Remote operation

Operation via HART protocol and FieldCare

Certificates and approvals

CE mark	The measuring system is in conformity with the statutory requirements of the EC Directives. Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
C-tick mark	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".
Ex approval	Information about currently available Ex versions (FM, CSA etc.) can be supplied by your Endress+Hauser Sales Center on request. All explosion protection data are given in a separate documentation which is available upon request.
Other standards and	■ EN 60529

quidelines

- Degrees of protection by housing (IP code).
- EN 61010

Protection Measures for Electrical Equipment for Measurement, Control, Regulation and Laboratory Procedures.

- IEC/EN 61326
 - "Emission in accordance with requirements for Class A". Electromagnetic compatibility (EMC requirements).
- ANSI/ISA-S82.01
 - Safety Standard for Electrical and Electronic Test, Measuring, Controlling and related Equipment -General Requirements. Pollution degree 2, Installation Category II.
- CAN/CSA-C22.2 No. 1010.1-92 Safety requirements for Electrical Equipment for Measurement and Control and Laboratory Use. Pollution degree 2, Installation Category II.

Pressure equipment directive

The measuring devices can be ordered with or without PED (Pressure Equipment Directive). If a device with PED is required, this must ordered explicitly. This is not possible or required for devices with nominal diameters of DN 25 (1") or smaller.

- With the identification PED/G1/III on the sensor nameplate, Endress+Hauser confirms conformity with the "Basic safety requirements" of Appendix I of the Pressure Equipment Directive 2014/68/EU.
- Devices with this identification (with PED) are suitable for the following types of fluid:
 - Fluids of Group 1 and 2 with a steam pressure of greater than, or smaller and equal to 0.5 bar (7.3
 - Unstable gases
- Devices without this identification (without PED) are designed and manufactured according to good engineering practice. They correspond to the requirements of Art.4, Section 3 of the Pressure Equipment Directive 2014/68/EU. Their application is illustrated in Diagrams 6 to 9 in Appendix II of the Pressure Equipment Directive 2014/68/EU.

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select country → Instruments → Select device → Product page function: Configure this product
- From your Endress+Hauser Sales Center: www.endress.com/worldwide

Product Configurator - the tool for individual product configuration:

Up-to-the-minute configuration data

- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Accessories

Various accessories, which can be ordered separately from Endress+Hauser, are available for the transmitter and the sensor. Your Endress+Hauser service organization can provide detailed information on the order codes in question.

Device-specific accessories

For the transmitter

Accessory	Description
Proline Promag 10 transmitter	Transmitter for replacement or storage. Use the order code to define the following specifications: Approvals Degree of protection/version Cable for remote version Cable entry Display/power supply/operation Software Outputs/inputs
Mounting set for Promag 10 transmitter	Mounting set for aluminum field housing (remote version). Suitable for Pipe mounting
Cable for remote version	Coil and electrode cables, various lengths.
Process display RIA45	Multifunctional 1-channel display unit: Universal input Transmitter power supply Limit relay Analog output
Process display RIA251	Digital display device for looping into the 4 to 20 mA current loop.
Field display unit RIA16	Digital field display device for looping into the 4 to 20 mA current loop.
Application Manager RMM621	Electronic recording, display, balancing, control, saving and event and alarm monitoring of analog and digital input signals. Values and conditions determined are output by means of analog and digital output signals. Remote transmission of alarms, input values and calculated values using a PSTN or GSM modem.

For the sensor

Accessory	Description
Wall-mounting kit for Promag H	Wall-mounting kit for the Promag H sensor.
Mounting kit for Promag D as wafer version	 Mounting bolts Nuts incl. washers Flange seals Centering sleeves (if required for the flange)
Set of seals for Promag D as wafer version	Set of seals consisting of two flange seals.
Mounting kit for Promag H	2 process connectionsThreaded fastenersSeals
Set of seals for Promag H	For regular replacement of the seals of the Promag H sensor.
Welding jig for Promag H	Weld nipple as process connection: welding jig for installation in pipe.

Accessory	Description
Adapter connection for Promag A/H	Adapter connections for installing a Promag H instead of a Promag 30/33A or Promag 30/33H DN 25.
Ground cable for Promag E/L/P/W	Ground cable for potential equalization.
Ground disk for Promag E/L/P/W	Ground disk for potential equalization.

Communication-specific accessories

Accessory	Description
HART Communicator Field Xpert SFX 100	Handheld terminal for remote configuration and for obtaining measured values via the HART current output (4 to 20 mA). Contact your Endress+Hauser representative for more information.
Fieldgate FXA320	Gateway for remote interrogation of HART sensors and actuators via Web browser: 2 - Cchannel analog input (4 to 20 mA) 4 binary inputs with event counter function and frequency measurement Communication via modem, Ethernet or GSM Visualization via Internet/Intranet in Web browser and/or WAP cellular phone Limit value monitoring with alarm by e-mail or SMS Synchronized time stamping of all measured values.
Fieldgate FXA520	Gateway for remote interrogation of HART sensors and actuators via Web browser: Web server for remote monitoring of up to 30 measuring points Intrinsically safe version [EEx ia]IIC for applications in hazardous areas Communication via modem, Ethernet or GSM Visualization via Internet/Intranet in Web browser and/or WAP cellular phone Limit value monitoring with alarm by e-mail or SMS Synchronized time stamping of all measured values Remote diagnosis and remote configuration of connected HART devices
FXA195	The Commubox FXA195 connects intrinsically safe Smart transmitters with HART protocol to the USB port of a personal computer. This makes the remote operation of the transmitters possible with the aid of configuration programs (e.g. FieldCare). Power is supplied to the Commubox by means of the USB port

Service-specific accessories

Accessory	Description
Applicator	Software for selecting and planning flowmeters. The Applicator software can be downloaded from the Internet or ordered on CD-ROM for installation on a local PC. Contact your Endress+Hauser representative for more information.
Fieldcheck	Tester/simulator for testing flowmeters in the field. When used in conjunction with the "FieldCare" software package, test results can be imported into a database, printed out and used for official certification. Contact your Endress+Hauser representative for more information.
FieldCare	FieldCare is Endress+Hauser's FDT-based asset management tool. It can configure all intelligent field units in your system and helps you manage them. By using status information, it is also a simple but effective way of checking their status and condition.

Accessory	Description
Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all the relevant process variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a DSD card or USB stick. Memograph M boasts a modular design, intuitive operation and a comprehensive security concept. The ReadWin® 2000 PC software is part of the standard package and is used for configuring, visualizing and archiving the data captured. The mathematics channels which are optionally available enable continuous monitoring of specific power consumption, boiler efficiency and other parameters which are important for efficient energy management.
FXA193	Service interface from the device to the PC for operation via FieldCare.

Documentation

- System Information Promag 10 (SI042D/06)
- Operating Instructions Promag 10 (BA00082D/06)

Registered trademarks

 $KALREZ^{\tiny{\tiny{\$}}}$ and $VITON^{\tiny{\$}}$

Registered trademarks of E.I. Du Pont de Nemours & Co., Wilmington, USA

TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA

HART[®]

Registered trademark of the HART Communication Foundation, Austin, USA

FieldCare®, Fieldcheck®, Field Xpert™, Applicator®

Registered or registration-pending trademarks of the Endress+Hauser Group



