# **Technical Information** Proline Promass F 200

Coriolis flowmeter

# Robust flowmeter with genuine loop-powered technology

## Application

- Measuring principle operates independently of physical fluid properties such as viscosity or density
- Highest measurement performance for liquids and gases in a wide range of applications

## Device properties

- Mass flow: measured error ±0.1 %
- Medium temperature: 205 °C (401 °F)
- Nominal diameter: DN 8 to 80 (<sup>3</sup>/<sub>8</sub> to 3")
- Loop-powered technology
- Robust: dual-compartment housing
- Plant safety: worldwide approvals (SIL, Haz. area)

## Your benefits

- Highest process safety immune to fluctuating and harsh environments
- Fewer process measuring points multivariable measurement (flow, density, temperature)
- Space-saving installation no in/outlet run needs
- Convenient device wiring separate connection compartment
- Safe operation no need to open the device due to display with touch control, background lighting
- Integrated verification Heartbeat Technology





71505583 2021-01-01

# Table of contents

| Document information   |  |
|--|--|
| Function and system design         Measuring principle         Measuring system         Safety   | .5<br>.6   |
| Input  | . 8<br>. 8   |
| Output .<br>Output signal .<br>Signal on alarm .<br>Load .<br>Ex connection data .<br>Low flow cut off .<br>Galvanic isolation .<br>Protocol-specific data . | 9<br>11<br>12<br>12<br>16<br>16<br>16  |
| Power supply   | 21<br>21<br>22<br>23<br>23<br>23<br>24<br>27<br>27<br>27<br>27<br>27<br>27<br>27 |
| Performance characteristics  |  |
| InstallationMounting locationOrientationInlet and outlet runsSpecial mounting instructions   | <b>32</b><br>33<br>34<br>34  |
| Environment  | <b>34</b><br>34<br>34<br>35  |

| Degree of protection   | 35<br>35<br>35<br>35<br>35<br>35  |
|--|---|
| Process .<br>Medium temperature range .<br>Density .<br>Pressure-temperature ratings .<br>Sensor housing .<br>Rupture disk .<br>Flow limit .<br>Pressure loss .<br>System pressure .<br>Thermal insulation .<br>Heating .<br>Vibrations .  | <b>35</b><br>35<br>35<br>40<br>41<br>41<br>42<br>42<br>42<br>42<br>42<br>42 |
| Mechanical construction  | <b>44</b><br>59<br>67<br>68<br>70<br>70                                     |
| Operability  | <b>70</b><br>70<br>71<br>72<br>74   |
| Certificates and approvals .<br>CE mark .<br>C-Tick symbol .<br>Functional safety .<br>Ex approval .<br>Sanitary compatibility .<br>Functional safety .<br>HART certification .<br>FOUNDATION Fieldbus certification .<br>Certification PROFIBUS .<br>Pressure Equipment Directive .<br>Other standards and guidelines . | <b>74</b><br>74<br>74<br>74<br>75<br>75<br>76<br>76<br>76<br>76<br>76       |
| Ordering information   | 77  |
| Application packages   | <b>77</b><br>77<br>78   |
| Accessories  | <b>78</b><br>78<br>79   |

| Service-specific accessories |    |
|------------------------------|----|
| Documentation                | 81 |
| Registered trademarks        | 82 |

# **Document information**

## Symbols used

## Electrical symbols

| Symbol   | Meaning  |
|----------|--|
|          | Direct current   |
| $\sim$   | Alternating current  |
| $\sim$   | Direct current and alternating current   |
| <u> </u> | <b>Ground connection</b><br>A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.  |
|          | Protective ground connection<br>A terminal which must be connected to ground prior to establishing any other<br>connections.   |
| Ą        | <b>Equipotential connection</b><br>A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice. |

## Symbols for certain types of information

| Symbol | Meaning  |
|--------|--|
|        | <b>Permitted</b><br>Procedures, processes or actions that are permitted. |
|        | <b>Preferred</b><br>Procedures, processes or actions that are preferred. |
| ×      | <b>Forbidden</b><br>Procedures, processes or actions that are forbidden. |
| i      | <b>Tip</b><br>Indicates additional information.                          |
|        | Reference to documentation   |
|        | Reference to page  |
|        | Reference to graphic   |
|        | Visual inspection  |

## Symbols in graphics


| Symbol         | Meaning                        |
|----------------|--------------------------------|
| 1, 2, 3,       | Item numbers                   |
| 1., 2., 3      | Series of steps                |
| A, B, C,       | Views                          |
| A-A, B-B, C-C, | Sections                       |
| EX             | Hazardous area                 |
| X              | Safe area (non-hazardous area) |
| ≈➡             | Flow direction                 |

## Function and system design

| Measuring principle | The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present in a system when both translational and rotational movements are superimposed.                      |
|---------------------|---|
|                     | $F_c = 2 \cdot \Delta m (v \cdot \omega)$   |
|                     | $F_c =$ Coriolis force  |
|                     | $\Delta m = moving mass$  |
|                     | $\omega = \text{ rotational velocity}$  |
|                     | v = radial velocity in rotating or oscillating system   |
|                     | The amplitude of the Coriolis force depends on the moving mass $\Delta m$ , its velocity v in the system and thus on the mass flow. Instead of a constant rotational velocity $\omega$ , the sensor uses oscillation. |
|                     | In the sensor, two parallel measuring tubes containing flowing fluid oscillate in antiphase, acting like a tuning fork. The Coriolis forces produced at the measuring tubes cause a phase shift in the tube           |

oscillations (see illustration):

- At zero flow (when the fluid is at a standstill) the two tubes oscillate in phase (1).
- Mass flow causes deceleration of the oscillation at the inlet of the tubes (2) and acceleration at the outlet (3).



The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube oscillations at the inlet and outlet. System balance is ensured by the antiphase oscillation of the two measuring tubes. The measuring principle operates independently of temperature, pressure, viscosity, conductivity and flow profile.

#### Density measurement

The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising measuring tube and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. Resonance frequency is thus a function of medium density. The microprocessor utilizes this relationship to obtain a density signal.

## Volume measurement

Together with the measured mass flow, this is used to calculate the volume flow.

#### **Temperature measurement**


The temperature of the measuring tube is determined in order to calculate the compensation factor due to temperature effects. This signal corresponds to the process temperature and is also available as an output signal.

## Measuring system


The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.

#### Transmitter



#### Sensor



#### Safety

#### IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

#### Device-specific IT security

The device offers a range of specific functions to support protective measures on the operator's side. These functions can be configured by the user and guarantee greater in-operation safety if used correctly. An overview of the most important functions is provided in the following section.

#### Protecting access via hardware write protection

Write access to the device parameters via the local display or operating tool (e.g. FieldCare, DeviceCare) can be disabled via a write protection switch (DIP switch on the motherboard). When hardware write protection is enabled, only read access to the parameters is possible.

Hardware write protection is disabled when the device is delivered.

## Protecting access via a password

A password can be used to protect against write access to the device parameters.

This password locks write access to the device parameters via the local display or another operating tool (e.g. FieldCare, DeviceCare) and, in terms of functionality, is equivalent to hardware write protection. If the service interface CDI RJ-45 is used, read access is only possible if the password is entered.

#### User-specific access code

Write access to the device parameters via the local display or operating tool (e.g. FieldCare, DeviceCare) can be protected by the modifiable, user-specific access code.

## Access via fieldbus

Cyclic fieldbus communication (read and write, e.g. measured value transmission) with a higherorder system is not affected by the restrictions mentioned above.

# Input

# Measured variable Direct measured variables • Mass flow • Density

Temperature

## Calculated measured variables

- Volume flow
- Corrected volume flow
- Reference density

## Measuring range

## Measuring ranges for liquids

| DN   |      | Measuring range full scal | e values $\dot{m}_{min(F)}$ to $\dot{m}_{max(F)}$ |
|------|------|---------------------------|---|
| [mm] | [in] | [kg/h]                    | [lb/min]  |
| 8    | 3⁄8  | 0 to 2 000                | 0 to 73.50  |
| 15   | 1/2  | 0 to 6 500                | 0 to 238.9  |
| 25   | 1    | 0 to 18000                | 0 to 661.5  |
| 40   | 11/2 | 0 to 45 000               | 0 to 1654   |
| 50   | 2    | 0 to 70 000               | 0 to 2 573  |
| 80   | 3    | 0 to 180 000              | 0 to 6615   |

#### Measuring ranges for gases

The full scale values depend on the density of the gas and can be calculated with the formula below:  $\dot{m}_{max(G)} = \dot{m}_{max(F)} \cdot \rho_G$ : x

| m <sub>max(G)</sub>                     | Maximum full scale value for gas [kg/h]                         |
|---|---|
| m <sub>max(F)</sub>                     | Maximum full scale value for liquid [kg/h]                      |
| $\dot{m}_{\max(G)} < \dot{m}_{\max(F)}$ | $\dot{m}_{max(G)}$ can never be greater than $\dot{m}_{max(F)}$ |
| ρ <sub>G</sub>                          | Gas density in [kg/m <sup>3</sup> ] at operating conditions     |
| x                                       | Constant dependent on nominal diameter                          |

| DN   |      | X                    |
|------|------|----------------------|
| [mm] | [in] | [kg/m <sup>3</sup> ] |
| 8    | 3⁄8  | 60                   |
| 15   | 1/2  | 80                   |
| 25   | 1    | 90                   |
| 40   | 1½   | 90                   |
| 50   | 2    | 90                   |
| 80   | 3    | 110                  |

To calculate the measuring range, use the Applicator sizing tool  $\rightarrow \cong 80$ 

## Calculation example for gas

Sensor: Promass F, DN 50

- Gas: Air with a density of 60.3 kg/m<sup>3</sup> (at 20  $^\circ\!C$  and 50 bar)
- Measuring range (liquid): 70000 kg/h
- $x = 90 \text{ kg/m}^3$  (for Promass F, DN 50)

|                     | Maximum possible full scale value:<br>$\dot{m}_{max(G)} = \dot{m}_{max(F)} \cdot \rho_G$ : x = 70000 kg/h · 60.3 kg/m <sup>3</sup> : 90 kg/m <sup>3</sup> = 46900 kg/h  |
|---------------------|---|
|                     | Recommended measuring range   |
|                     | "Flow limit" section $\rightarrow \square 41$   |
| Operable flow range | Over 1000 : 1.  |
|                     | Flow rates above the preset full scale value do not override the electronics unit, with the result that the totalizer values are registered correctly.  |
| Input signal        | External measured values  |
|                     | To increase the accuracy of certain measured variables or to calculate the corrected volume flow for gases, the automation system can continuously write the operating pressure to the measuring device. Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S. |
|                     | Yarious pressure transmitters and temperature measuring devices can be ordered from Endress +Hauser: see "Accessories" section → 🗎 80   |
|                     | It is recommended to read in external measured values to calculate the following measured variables:<br>Mass flow Corrected volume flow   |
|                     | HART protocol   |
|                     | The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:<br>• HART protocol<br>• Burst mode   |
|                     | Digital communication   |
|                     | The measured values can be written from the automation system to the measuring via:<br>• FOUNDATION Fieldbus<br>• PROFIBUS PA   |

# Output

## Output signal

## **Current output**

| Current output 1                 | 4-20 mA HART (passive)   |
|----------------------------------|--|
| Current output 2                 | 4-20 mA (passive)  |
| Resolution                       | < 1 µA   |
| Damping                          | Adjustable: 0.0 to 999.9 s   |
| Assignable measured<br>variables | <ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> </ul> |

## Pulse/frequency/switch output

| Function | Can be set to pulse, frequency or switch output |
|----------|---|
| Version  | Passive, open collector                         |

| Maximum input values             | <ul> <li>DC 35 V</li> <li>50 mA</li> </ul>   |  |
|----------------------------------|--|--|
|                                  | For information on the Ex connection values $\rightarrow \equiv 12$  |  |
|                                  |  |  |
| Voltage drop                     | <ul> <li>For ≤ 2 mA: 2 V</li> <li>For 10 mA: 8 V</li> </ul>  |  |
| Residual current                 | ≤ 0.05 mA  |  |
| Pulse output                     |  |  |
| Pulse width                      | Adjustable: 5 to 2 000 ms  |  |
| Maximum pulse rate               | 100 Impulse/s  |  |
| Pulse value                      | Adjustable   |  |
| Assignable measured<br>variables | <ul><li>Mass flow</li><li>Volume flow</li><li>Corrected volume flow</li></ul>  |  |
| Frequency output                 | requency output  |  |
| Output frequency                 | Adjustable: 0 to 1 000 Hz  |  |
| Damping                          | Adjustable: 0 to 999 s   |  |
| Pulse/pause ratio                | 1:1  |  |
| Assignable measured<br>variables | <ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> </ul>   |  |
| Switch output                    |  |  |
| Switching behavior               | Binary, conductive or non-conductive   |  |
| Switching delay                  | Adjustable: 0 to 100 s   |  |
| Number of switching cycles       | Unlimited  |  |
| Assignable functions             | <ul> <li>Off</li> <li>On</li> <li>Diagnostic behavior</li> <li>Limit value <ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>Totalizer 1-3</li> </ul> </li> <li>Flow direction monitoring</li> <li>Status <ul> <li>Partially filled pipe detection</li> <li>Low flow cut off</li> </ul> </li> </ul> |  |

## FOUNDATION Fieldbus

| Signal encoding | Manchester Bus Powered (MBP) |
|-----------------|------------------------------|
| Data transfer   | 31.25 KBit/s, Voltage mode   |

## PROFIBUS PA

| Signal encoding | Manchester Bus Powered (MBP) |
|-----------------|------------------------------|
| Data transfer   | 31.25 KBit/s, Voltage mode   |

## Signal on alarm

Depending on the interface, failure information is displayed as follows:

## Current output 4 to 20 mA

## 4 to 20 mA

| Failure mode | <ul> <li>Choose from:</li> <li>4 to 20 mA in accordance with NAMUR recommendation NE 43</li> <li>4 to 20 mA in accordance with US</li> <li>Min. value: 3.59 mA</li> <li>Max. value: 22.5 mA</li> <li>Freely definable value between: 3.59 to 22.5 mA</li> <li>Actual value</li> <li>Last valid value</li> </ul> |
|--------------|---|
|--------------|---|

## Pulse/frequency/switch output

| Pulse output     |   |  |
|------------------|---|--|
| Failure mode     | Choose from:<br>• Actual value<br>• No pulses                             |  |
| Frequency output |   |  |
| Failure mode     | Choose from:<br>• Actual value<br>• 0 Hz<br>• Defined value: 0 to 1250 Hz |  |
| Switch output    |   |  |
| Failure mode     | Choose from:<br>• Current status<br>• Open<br>• Closed                    |  |

## **FOUNDATION Fieldbus**

| Status and alarm messages                             | Diagnostics in accordance with FF-891 |
|---|---------------------------------------|
| Error current FDE (Fault<br>Disconnection Electronic) | 0 mA                                  |

## PROFIBUS PA

| Status and alarm<br>messages                          | Diagnostics in accordance with PROFIBUS PA Profile 3.02 |
|---|---|
| Error current FDE (Fault<br>Disconnection Electronic) | 0 mA  |

## Local display

| Plain text display | With information on cause and remedial measures   |
|--------------------|---|
| Backlight          | Additionally for device version with SD03 local display: red lighting indicates a device error. |

Status signal as per NAMUR recommendation NE 107

#### Interface/protocol

- Via digital communication:
  - HART protocol
  - FOUNDATION Fieldbus
  - PROFIBUS PA
- Via service interface

| Plain text display With in | formation on cause and remedial measures |
|----------------------------|--|
|----------------------------|--|


Additional information on remote operation  $\rightarrow \cong 72$ 

Load for current output: 0 to 500  $\Omega,$  depending on the external supply voltage of the power supply unit

#### Calculation of the maximum load

Depending on the supply voltage of the power supply unit ( $U_S$ ), the maximum load ( $R_B$ ) including line resistance must be observed to ensure adequate terminal voltage at the device. In doing so, observe the minimum terminal voltage

- For  $U_S = 17.9$  to 18.9 V:  $R_B \le (U_S 17.9$  V): 0.0036 A
- For  $U_s = 18.9$  to 24 V:  $R_B \le (U_s 13 \text{ V}): 0.022 \text{ A}$
- For  $U_s = \ge 24 \text{ V}$ :  $R_B \le 500 \Omega$



- A Operating range for order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/ frequency/switch output" with Ex i and option C "4-20 mA HART + 4-20 mA analog"
- B Operating range for order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/ frequency/switch output" with non-Ex and Ex d

#### Sample calculation

Supply voltage of the power supply unit:  $U_S = 19 \text{ V}$ Maximum load:  $R_B \le (19 \text{ V} - 13 \text{ V}): 0.022 \text{ A} = 273 \Omega$ 

#### Ex connection data

Load

## Safety-related values

Type of protection Ex d

| Order code for "Output" | Output type                   | Safety-related values                                     |
|-------------------------|-------------------------------|---|
| Option <b>A</b>         | 4-20mA HART                   | U <sub>nom</sub> = DC 35 V<br>U <sub>max</sub> = 250 V    |
| Option <b>B</b>         | 4-20mA HART                   | U <sub>nom</sub> = DC 35 V<br>U <sub>max</sub> = 250 V    |
|                         | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |

| Order code for "Output" | Output type                   | Safety-related values                                     |
|-------------------------|-------------------------------|---|
| Option C                | 4-20mA HART                   | U <sub>nom</sub> = DC 30 V                                |
|                         | 4-20mA analog                 | U <sub>max</sub> = 250 V                                  |
| Option <b>E</b>         | FOUNDATION Fieldbus           | $U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$  |
|                         | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |
| Option <b>G</b>         | PROFIBUS PA                   | $U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$  |
|                         | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |

1) Internal circuit limited by  $R_i$  = 760.5  $\Omega$ 

## Ex nA type of protection

| Order code for "Output" | Output type                   | Safety-related values   |
|-------------------------|-------------------------------|---|
| Option A                | 4-20mA HART                   | U <sub>nom</sub> = DC 35 V<br>U <sub>max</sub> = 250 V  |
| Option <b>B</b>         | 4-20mA HART                   | U <sub>nom</sub> = DC 35 V<br>U <sub>max</sub> = 250 V  |
|                         | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$  |
| Option C                | 4-20mA HART                   | U <sub>nom</sub> = DC 30 V  |
|                         | 4-20mA analog                 | U <sub>max</sub> = 250 V  |
| Option <b>E</b>         | FOUNDATION Fieldbus           | $U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$  |
|                         | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$   |
| Option <b>G</b>         | PROFIBUS PA                   | $U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$  |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_{nom} = DC \ 35 \ V \\ U_{max} = 250 \ V \\ P_{max} = 1 \ W^{1)} \end{array}$ |

1) Internal circuit limited by  $R_i = 760.5 \ \Omega$ 

## Type of protection XP

| Order code for "Output" | Output type                   | Safety-related values   |
|-------------------------|-------------------------------|---|
| Option A                | 4-20mA HART                   | U <sub>nom</sub> = DC 35 V<br>U <sub>max</sub> = 250 V  |
| Option <b>B</b>         | 4-20mA HART                   | U <sub>nom</sub> = DC 35 V<br>U <sub>max</sub> = 250 V  |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_{nom} = DC \ 35 \ V \\ U_{max} = 250 \ V \\ P_{max} = 1 \ W^{1)} \end{array}$ |

| Order code for "Output" | Output type                   | Safety-related values                                     |
|-------------------------|-------------------------------|---|
| Option C                | 4-20mA HART                   | $U_{nom} = DC 30 V$                                       |
|                         | 4-20mA analog                 | U <sub>max</sub> = 250 V                                  |
| Option <b>E</b>         | FOUNDATION Fieldbus           | $U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$  |
|                         | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |
| Option <b>G</b>         | PROFIBUS PA                   | $U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$  |
|                         | Pulse/frequency/switch output | $U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$ |

1) Internal circuit limited by  $R_i = 760.5 \ \Omega$ 

## Intrinsically safe values

Type of protection Ex ia

| Order code for "Output" | Output type                   | Intrinsically safe   | values  |
|-------------------------|-------------------------------|--|---|
| Option <b>A</b>         | 4-20mA HART                   | $ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = 300 \; mA \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 5 \; nF \end{array} $             |   |
| Option <b>B</b>         | 4-20mA HART                   | $ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 5 \; nF \end{array} $ |   |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = 300 \; mA \\ P_{i} = 1 \; W \\ L_{i} = 0 \; \mu H \\ C_{i} = 6 \; nF \end{array}$     |   |
| Option C                | 4-20mA HART                   | $ \begin{array}{c} U_i = DC \; 30 \; V \\ I_i = 300 \; mA \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 30 \; nF \end{array} $            |   |
|                         | 4-20mA analog                 |  |   |
| Option <b>E</b>         | FOUNDATION Fieldbus           |  | $      FISCO \\ U_i = 17.5 V \\ l_i = 550 mA \\ P_i = 5.5 W \\ L_i = 10 \ \mu H \\ C_i = 5 \ nF $ |
|                         | Pulse/frequency/switch output | $ \begin{array}{l} U_i = 30 \ V \\ l_i = 300 \ mA \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array} $                        |   |

| Order code for "Output" | Output type                   | Intrinsically safe  | values  |
|-------------------------|-------------------------------|---|---|
|                         | PROFIBUS PA                   |   | $      FISCO \\       U_i = 17.5 V \\       l_i = 550 mA \\       P_i = 5.5 W \\       L_i = 10 \ \mu H \\       C_i = 5 nF $ |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_i = 30 \ V \\ l_i = 300 \ mA \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array}$ |   |

## Type of protection Ex ic

| Order code for "Output" | Output type                   | Intrinsically safe v   | alues   |  |
|-------------------------|-------------------------------|--|---|--|
| Option <b>A</b>         | 4-20mA HART                   | $\begin{array}{l} U_{i} = DC \ 35 \ V \\ I_{i} = n.a. \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 5 \ nF \end{array}$ |   |  |
| Option <b>B</b>         | 4-20mA HART                   | $U_i = DC 35 V$ $I_i = n.a.$ $P_i = 1 W$ $L_i = 0 \mu H$ $C_i = 5 nF$  |   |  |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_i = DC \ 35 \ V \\ I_i = n.a. \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array}$           | $ \begin{array}{l} I_i = n.a. \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \end{array} $               |  |
| Option C                | 4-20mA HART                   | U <sub>i</sub> = DC 30 V   |   |  |
|                         | 4-20mA analog                 | $ I_i = n.a.  P_i = 1 W  L_i = 0 \mu H  C_i = 30 nF $  |   |  |
| Option <b>E</b>         | FOUNDATION Fieldbus           | $\begin{array}{l} U_{i} = 32 \ V \\ l_{i} = 300 \ mA \\ P_{i} = n.a. \\ L_{i} = 10 \ \mu H \end{array}$                    | FISCO<br>$U_i = 17.5 V$<br>$l_i = n.a.$<br>$P_i = n.a.$<br>$L_i = 10 \mu H$<br>$C_i = 5 nF$ |  |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_{i} = 35 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$  |   |  |
| Option <b>G</b>         | PROFIBUS PA                   | $ \begin{array}{l} U_{i} = 32 \ V \\ l_{i} = 300 \ mA \\ P_{i} = n.a. \\ L_{i} = 10 \ \mu H \end{array} $                  | FISCO<br>$U_i = 17.5 V$<br>$l_i = n.a.$<br>$P_i = n.a.$<br>$L_i = 10 \mu H$<br>$C_i = 5 nF$ |  |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_{i} = 35 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$  |   |  |

| Order code for "Output" | Output type                   | Intrinsically safe values   |
|-------------------------|-------------------------------|---|
| Option <b>A</b>         | 4-20mA HART                   | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = 300 \; mA \\ P_{i} = 1 \; W \\ L_{i} = 0 \; \mu H \\ C_{i} = 5 \; nF \end{array}$  |
| Option <b>B</b>         | 4-20mA HART                   | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = 300 \; mA \\ P_{i} = 1 \; W \\ L_{i} = 0 \; \mu H \\ C_{i} = 5 \; nF \end{array}$  |
|                         | Pulse/frequency/switch output | $\begin{array}{l} U_{i} = DC \; 30 \; V \\ I_{i} = 300 \; mA \\ P_{i} = 1 \; W \\ L_{i} = 0 \; \mu H \\ C_{i} = 6 \; nF \end{array}$  |
| Option C                | 4-20mA HART                   | $U_i = DC 30 V$   |
|                         | 4-20mA analog                 | $ I_i = 300 \text{ mA}  P_i = 1 W  L_i = 0 \mu H  C_i = 30 \text{ nF} $   |
| Option E                | FOUNDATION Fieldbus           | $\begin{array}{ll} \mbox{STANDARD} & \mbox{FISCO} \\ U_i = 30 \ V & U_i = 17.5 \ V \\ l_i = 300 \ mA & l_i = 550 \ mA \\ P_i = 1.2 \ W & P_i = 5.5 \ W \\ L_i = 10 \ \mu H & L_i = 10 \ \mu H \\ C_i = 5 \ nF & C_i = 5 \ nF \end{array}$ |
|                         | Pulse/frequency/switch output | $ \begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array} $   |
| Option <b>G</b>         | PROFIBUS PA                   | $\begin{array}{ll} \mbox{STANDARD} & \mbox{FISCO} \\ U_i = 30 \ V & U_i = 17.5 \ V \\ l_i = 300 \ mA & l_i = 550 \ mA \\ P_i = 1.2 \ W & P_i = 5.5 \ W \\ L_i = 10 \ \mu H & L_i = 10 \ \mu H \\ C_i = 5 \ nF & C_i = 5 \ nF \end{array}$ |
|                         | Pulse/frequency/switch output | $ \begin{array}{l} U_i = 30 \ V \\ l_i = 300 \ mA \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array} $   |

Low flow cut off

The switch points for low flow cut off are user-selectable.

All outputs are galvanically isolated from one another.

Galvanic isolation Protocol-specific data

HART

| Manufacturer ID                       | 0x11   |
|---------------------------------------|--|
| Device type ID                        | 0x54   |
| HART protocol revision                | 7  |
| Device description files<br>(DTM, DD) | Information and files under:<br>www.endress.com    |
| HART load                             | <ul> <li>Min. 250 Ω</li> <li>Max. 500 Ω</li> </ul> |

| Dynamic variables | Read out the dynamic variables: HART command 3<br>The measured variables can be freely assigned to the dynamic variables.  |
|-------------------|--|
|                   | Measured variables for PV (primary dynamic variable) Mass flow Volume flow Corrected volume flow Density Reference density Temperature Carrier pipe temperature Electronic temperature Oscillation frequency Oscillation amplitude Oscillation damping |
|                   | <ul> <li>Signal asymmetry</li> <li>Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable)</li> <li>Mass flow</li> </ul>   |
|                   | <ul> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> </ul>  |
|                   | <ul> <li>Carrier pipe temperature</li> <li>Electronic temperature</li> <li>Oscillation frequency</li> <li>Oscillation amplitude</li> <li>Oscillation damping</li> </ul>  |
|                   | <ul> <li>Signal asymmetry</li> <li>External pressure</li> <li>Totalizer 1</li> <li>Totalizer 2</li> <li>Totalizer 3</li> </ul>   |
| Device variables  | Read out the device variables: HART command 9<br>The device variables are permanently assigned.  |

## FOUNDATION Fieldbus

| Manufacturer ID                               | 0x452B48   |
|---|--|
| Ident number                                  | 0x1054   |
| Device revision                               | 1  |
| DD revision                                   | Information and files under:   |
| CFF revision                                  | <ul><li>www.endress.com</li><li>www.fieldbus.org</li></ul>                         |
| Device Tester Version (ITK version)           | 6.1.1  |
| ITK Test Campaign Number                      | IT094200   |
| Link Master capability (LAS)                  | Yes  |
| Choice of "Link Master" and<br>"Basic Device" | Yes<br>Factory setting: Basic Device   |
| Node address                                  | Factory setting: 247 (0xF7)  |
| Supported functions                           | The following methods are supported:<br>• Restart<br>• ENP Restart<br>• Diagnostic |
| Virtual Communication Relationships (VCRs)    |  |
| Number of VCRs                                | 44   |
| Number of link objects in VFD                 | 50   |
| Permanent entries                             | 1  |

| Client VCRs              | 0      |
|--------------------------|--------|
| Server VCRs              | 10     |
| Source VCRs              | 43     |
| Sink VCRs                | 0      |
| Subscriber VCRs          | 43     |
| Publisher VCRs           | 43     |
| Device Link Capabilities |        |
| Slot time                | 4      |
| Min. delay between PDU   | 8      |
| Max. response delay      | Min. 5 |

## Transducer Blocks

| Block  | Contents   | Output values  |
|--|--|--|
| Setup Transducer Block<br>(TRDSUP)                         | All parameters for standard commissioning.   | No output values   |
| Advanced Setup<br>Transducer Block<br>(TRDASUP)            | All parameters for more accurate measurement configuration.  | No output values   |
| Display Transducer<br>Block<br>(TRDDISP)                   | Parameters for configuring the local display.  | No output values   |
| HistoROM Transducer<br>Block<br>(TRDHROM)                  | Parameters for using the HistoROM function.  | No output values   |
| Diagnostic Transducer<br>Block<br>(TRDDIAG)                | Diagnostics information.   | <ul> <li>Process variables (AI Channel)</li> <li>Temperature (7)</li> <li>Volume flow (9)</li> <li>Mass flow (11)</li> <li>Corrected volume flow (13)</li> <li>Density (14)</li> <li>Reference density (15)</li> </ul> |
| Expert Configuration<br>Transducer Block<br>(TRDEXP)       | Parameters that require the user to have in-<br>depth knowledge of the operation of the device<br>in order to configure the parameters<br>appropriately. | No output values   |
| Expert Information<br>Transducer Block<br>(TRDEXPIN)       | Parameters that provide information about the state of the device.   | No output values   |
| Service Sensor<br>Transducer Block<br>(TRDSRVS)            | Parameters that can only be accessed by Endress<br>+Hauser Service.  | No output values   |
| Service Information<br>Transducer Block<br>(TRDSRVIF)      | Parameters that provide Endress+Hauser Service<br>with information about the state of the device.  | No output values   |
| Total Inventory<br>Counter Transducer<br>Block<br>(TRDTIC) | Parameters for configuring all the totalizers and the inventory counter.   | Process variables (AI Channel)<br>• Totalizer 1 (16)<br>• Totalizer 2 (17)<br>• Totalizer 3 (18)   |
| Heartbeat Technology<br>Transducer Block<br>(TRDHBT)       | Parameters for the configuration and<br>comprehensive information about the results of<br>the verification.  | No output values   |
| Heartbeat Results 1<br>Transducer Block<br>(TRDHBTR1)      | Information about the results of the verification.   | No output values   |

| Block   | Contents   | Output values    |
|---|--|------------------|
| Heartbeat Results 2<br>Transducer Block<br>(TRDHBTR2) | Information about the results of the verification. | No output values |
| Heartbeat Results 3<br>Transducer Block<br>(TRDHBTR3) | Information about the results of the verification. | No output values |
| Heartbeat Results 4<br>Transducer Block<br>(TRDHBTR4) | Information about the results of the verification. | No output values |

## Function blocks

| Block                                    | Number<br>of<br>blocks | Contents   | Process variables (Channel)  |
|--|------------------------|--|--|
| Resource Block<br>(RB)                   | 1                      | This Block (extended functionality) contains<br>all the data that uniquely identify the device; it<br>is the equivalent of an electronic nameplate<br>for the device.  | -  |
| Analog Input<br>Block<br>(AI)            | 6                      | This Block (extended functionality) receives<br>the measurement data provided by the Sensor<br>Block (can be selected via a channel number)<br>and makes the data available for other blocks<br>at the output.<br><b>Execution time:</b> 27 ms | <ul> <li>Temperature (7)</li> <li>Volume flow (9)</li> <li>Mass flow (11)</li> <li>Corrected volume flow (13)</li> <li>Density (14)</li> <li>Reference density (15)</li> <li>Totalizer 1 (16)</li> <li>Totalizer 2 (17)</li> <li>Totalizer 3 (18)</li> </ul> |
| Discrete Input<br>Block<br>(DI)          | 2                      | This Block (standard functionality) receives a discrete value (e.g. indicator that measuring range has been exceeded) and makes the value available for other blocks at the output. <b>Execution time:</b> 19 ms                               | <ul> <li>Switch output state (101)</li> <li>Empty pipe detection (102)</li> <li>Low flow cut off (103)</li> <li>Status verification (105)</li> </ul>   |
| PID Block<br>(PID)                       | 1                      | This Block (standard functionality) acts as a<br>proportional-integral-differential controller<br>and can be used universally for control in the<br>field. It enables cascading and feedforward<br>control.<br><b>Execution time:</b> 25 ms    | -  |
| Multiple Analog<br>Output Block<br>(MAO) | 1                      | This Block (standard functionality) receives<br>several analog values and makes them<br>available for other blocks at the output.<br><b>Execution time:</b> 22 ms  | <ul> <li>Channel_0 (121)</li> <li>Value 1: External compensation variable, pressure</li> <li>Value 2 to 8: Not assigned</li> <li>The pressure must be transmitted to the device in the SI basic unit.</li> </ul>   |

| Block                                     | Number<br>of<br>blocks | Contents   | Process variables (Channel)  |
|---|------------------------|--|--|
| Multiple Digital<br>Output Block<br>(MDO) | 1                      | This Block (standard functionality) receives<br>several discrete values and makes them<br>available for other blocks at the output.<br><b>Execution time:</b> 19 ms  | Channel_DO (122)  Value 1: Reset totalizer 1 Value 2: Reset totalizer 2 Value 3: Reset totalizer 3 Value 4: Flow override Value 5: Start heartbeat verification Value 6: Status switch output Value 7: Start zero point adjustment Value 8: Not assigned |
| Integrator Block<br>(IT)                  | 1                      | This Block (standard functionality) integrates<br>a measured variable over time or totalizes the<br>pulses from a Pulse Input Block. The Block can<br>be used as a totalizer that totalizes until a<br>reset, or as a batch totalizer whereby the<br>integrated value is compared against a target<br>value generated before or during the control<br>routine and generates a binary signal when<br>the target value is reached.<br><b>Execution time:</b> 21 ms | _  |

## PROFIBUS PA

| Manufacturer ID   | 0x11  |
|---|---|
| Ident number  | 0x155F  |
| Profile version   | 3.02  |
| Device description files (GSD,<br>DTM, DD)                              | Information and files under:<br>• www.endress.com<br>• www.profibus.org   |
| <b>Output values</b><br>(from measuring device to<br>automation system) | Analog input 1 to 6<br>Mass flow<br>Volume flow<br>Corrected volume flow<br>Density<br>Reference density<br>Temperature                     |
|   | Digital input 1 to 2<br>• Empty pipe detection<br>• Low flow cut off<br>• Status switch output<br>• Status verification<br>Totalizer 1 to 3 |
|   | <ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> </ul>   |


| Input values<br>(from automation system to<br>measuring device) | Analog output<br>External pressure<br>Digital output 1 to 4 (fixed assignment)<br>• Digital output 1: switch positive zero return on/off<br>• Digital output 2: switch zero point adjustment on/off<br>• Digital output 3: switch switch output on/off<br>• Digital output 4: start verification   |
|---|--|
|   | Totalizer 1 to 3<br>• Totalize<br>• Reset and hold<br>• Preset and hold<br>• Operating mode configuration:<br>• Net flow total<br>• Forward flow total<br>• Reverse flow total   |
| Supported functions   | <ul> <li>Identification &amp; Maintenance<br/>Simplest device identification on the part of the control system and<br/>nameplate</li> <li>PROFIBUS upload/download<br/>Reading and writing parameters is up to ten times faster with PROFIBUS<br/>upload/download</li> <li>Condensed status<br/>Simplest and self-explanatory diagnostic information by categorizing<br/>diagnostic messages that occur</li> </ul> |
| Configuration of the device<br>address                          | <ul> <li>DIP switches on the I/O electronics module</li> <li>Local display</li> <li>via operating tools (e.g. FieldCare)</li> </ul>  |

# Power supply

## Terminal assignment

## Transmitter

## Connection versions



| Order code for "Output"   | Terminal numbers       |       |             |                          |  |
|---------------------------|------------------------|-------|-------------|--------------------------|--|
|                           | Output 1               |       | Output 2    |                          |  |
|                           | 1 (+)                  | 2 (-) | 3 (+)       | 4 (-)                    |  |
| Option <b>A</b>           | 4-20 mA HART (passive) |       | -           |                          |  |
| Option $\mathbf{B}^{(1)}$ | 4-20 mA HART (passive) |       |             | y/switch output<br>sive) |  |
| Option $C^{(1)}$          | 4-20 mA HART (passive) |       | 4-20 mA ana | alog (passive)           |  |

| Order code for "Output"         | Terminal numbers    |       |          |                          |  |
|---------------------------------|---------------------|-------|----------|--------------------------|--|
|                                 | Output 1            |       | Output 2 |                          |  |
|                                 | 1 (+)               | 2 (-) | 3 (+)    | 4 (-)                    |  |
| Option $\mathbf{E}^{(1)(2)}$    | FOUNDATION Fieldbus |       | · · ·    | y/switch output<br>sive) |  |
| Option <b>G</b> <sup>1)3)</sup> | PROFIBUS PA         |       | _ · ·    | y/switch output<br>sive) |  |

Output 1 must always be used; output 2 is optional. FOUNDATION Fieldbus with integrated reverse polarity protection. PROFIBUS PA with integrated reverse polarity protection.

1) 2) 3)

## Pin assignment, device plug

PROFIBUS PA

| Pin |   | Assignment    | Coding | Plug/socket |
|-----|---|---------------|--------|-------------|
| 1   | + | PROFIBUS PA + | A      | Plug        |
| 2   |   | Grounding     |        |             |
| 3   | - | PROFIBUS PA – |        |             |
| 4   |   | Not assigned  |        |             |

## **FOUNDATION Fieldbus**

| Pin |   | Assignment   | Coding | Plug/socket |
|-----|---|--------------|--------|-------------|
| 1   | + | Signal +     | А      | Plug        |
| 2   | - | Signal –     |        |             |
| 3   |   | Grounding    |        |             |
| 4   |   | Not assigned |        |             |

## Supply voltage

## Transmitter

An external power supply is required for each output.

| Order code for "Output"  | Minimum<br>terminal voltage   | Maximum<br>terminal voltage |
|--|---|-----------------------------|
| Option <b>A</b> <sup>1) 2)</sup> : 4-20 mA HART                                    | <ul> <li>For 4 mA: ≥ DC 17.9 V</li> <li>For 20 mA: ≥ DC 13.5 V</li> </ul> | DC 35 V                     |
| Option <b>B</b> <sup>1) 2)</sup> : 4-20 mA HART, pulse/frequency/<br>switch output | <ul> <li>For 4 mA: ≥ DC 17.9 V</li> <li>For 20 mA: ≥ DC 13.5 V</li> </ul> | DC 35 V                     |
| Option <b>C</b> <sup>1)</sup> <sup>2)</sup> : 4-20 mA HART + 4-20 mA analog        | <ul> <li>For 4 mA: ≥ DC 17.9 V</li> <li>For 20 mA: ≥ DC 13.5 V</li> </ul> | DC 30 V                     |

| Order code for "Output"  | Minimum<br>terminal voltage | Maximum<br>terminal voltage |
|--|-----------------------------|-----------------------------|
| Option <b>E</b> <sup>3)</sup> : FOUNDATION Fieldbus, pulse/<br>frequency/switch output | ≥ DC 9 V                    | DC 32 V                     |
| Option <b>G</b> <sup>3</sup> : PROFIBUS PA, pulse/frequency/switch output              | ≥ DC 9 V                    | DC 32 V                     |

1) External supply voltage of the power supply unit with load.

2) For device versions with SD03 local display: The terminal voltage must be increased by DC 2 V if backlighting is used.

3) For device version with SD03 local display: The terminal voltage must be increased by DC 0.5 V if backlighting is used.



1

For information about the load see  $\rightarrow$   $\square$  12



For information on the Ex connection values  $\rightarrow \implies 12$ 

Power consumption

## Transmitter


| Order code for "Output"  | Maximum power consumption   |
|--|---|
| Option A: 4-20 mA HART   | 770 mW  |
| Option <b>B</b> : 4-20 mA HART, pulse/<br>frequency/switch output        | <ul><li>Operation with output 1: 770 mW</li><li>Operation with output 1 and 2: 2 770 mW</li></ul> |
| Option <b>C</b> : 4-20 mA HART + 4-20 mA<br>analog                       | <ul><li>Operation with output 1: 660 mW</li><li>Operation with output 1 and 2: 1 320 mW</li></ul> |
| Option <b>E</b> : FOUNDATION Fieldbus, pulse/<br>frequency/switch output | <ul><li>Operation with output 1: 576 mW</li><li>Operation with output 1 and 2: 2 576 mW</li></ul> |
| Option <b>G</b> : PROFIBUS PA, pulse/frequency/<br>switch output         | <ul><li>Operation with output 1: 512 mW</li><li>Operation with output 1 and 2: 2 512 mW</li></ul> |

For information on the Ex connection values  $\rightarrow \cong 12$ 

| Current consumption  | Current output   |  |  |  |
|----------------------|--|--|--|--|
|                      | For every 4-20 mA or 4-20 mA HART current output: 3.6 to 22.5 mA   |  |  |  |
|                      | If the option <b>Defined value</b> is selected in the <b>Failure mode</b> parameter : 3.59 to 22.5 mA  |  |  |  |
|                      | PROFIBUS PA  |  |  |  |
|                      | 16 mA  |  |  |  |
|                      | FOUNDATION Fieldbus  |  |  |  |
|                      | 18 mA  |  |  |  |
| Power supply failure | <ul> <li>Totalizers stop at the last value measured.</li> <li>Configuration is retained in the device memory (HistoROM).</li> <li>Error messages (incl. total operated hours) are stored.</li> </ul> |  |  |  |

## **Electrical connection**

## Connecting the transmitter




1 Cable entry for output 1

2 Cable entry for output 2

## **Connection examples**


Current output 4-20 mA HART



■ 1 Connection example for 4 to 20 mA HART current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications  $\rightarrow \square 27$
- 4 Analog display unit: observe maximum load  $\rightarrow \square 12$
- 5 Transmitter


## Pulse/frequency output



☑ 2 Connection example for pulse/frequency output (passive)

- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values  $\rightarrow \square 9$


## Switch output



🛃 3 Connection example for switch output (passive)

- Automation system with switch input (e.g. PLC) 1
- 2 Power supply
- 3 *Transmitter: Observe input values*  $\rightarrow \square 9$


## PROFIBUS-PA



€ 4 Connection example for PROFIBUS-PA

- 1 Control system (e.g. PLC)
- PROFIBUS PA segment coupler
- 2 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line


#### FOUNDATION Fieldbus



🛃 5 Connection example for FOUNDATION Fieldbus

- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus) 2
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- Measuring device Local grounding 5
- 6
- Bus terminator 7
- Potential matching line 8

#### HART input



- 🖻 6 *Connection example for HART input with a common negative (passive)*
- 1 Automation system with HART output (e.g. PLC)
- Active barrier for power supply (e.g. RN221N) 2
- Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable 3 specifications
- 4 Analog display unit: observe maximum load  $\rightarrow \cong 12$
- 5 Pressure measuring device (e.g. Cerabar M, Cerabar S): see requirements
- 6 Transmitter

| Potential equalization | Requirements   |  |  |  |
|------------------------|--|--|--|--|
|                        | No special measures for pote   | ential equalization are required.  |  |  |
|                        | For devices intended fo documentation (XA).  | r use in hazardous locations, please observe the guidelines in the Ex                                      |  |  |
| <b>Ferminals</b>       | <ul> <li>For device version without integrated overvoltage protection: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm<sup>2</sup> (20 to 14 AWG)</li> <li>For device version with integrated overvoltage protection: screw terminals for wire cross-sections 0.2 to 2.5 mm<sup>2</sup> (24 to 14 AWG)</li> </ul> |  |  |  |
| Cable entries          | <ul> <li>Cable gland (not for Ex d): M20 × 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in)</li> <li>Thread for cable entry: <ul> <li>For non-Ex and Ex: NPT ½"</li> <li>For non-Ex and Ex (not for CSA Ex d/XP): G ½"</li> <li>For Ex d: M20 × 1.5</li> </ul> </li> </ul>  |  |  |  |
| able specification     | Permitted temperature ran  | ge   |  |  |
|                        | Minimum requirement: cable   | e temperature range $\geq$ ambient temperature +20 K   |  |  |
|                        | Signal cable   |  |  |  |
|                        | Current output 4 to 20 mA HART   |  |  |  |
|                        | A shielded cable is recommended. Observe grounding concept of the plant.   |  |  |  |
|                        | Current output 4 to 20 mA  |  |  |  |
|                        | Standard installation cable is sufficient.   |  |  |  |
|                        | Pulse/frequency/switch output  |  |  |  |
|                        | Standard installation cable is sufficient.   |  |  |  |
|                        | FOUNDATION Fieldbus  |  |  |  |
|                        | Twisted, shielded two-wire cable.  |  |  |  |
|                        | For further information  | on planning and installing FOUNDATION Fieldbus networks see:   |  |  |
|                        | <ul> <li>Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)</li> <li>FOUNDATION Fieldbus Guideline</li> <li>IEC 61158-2 (MBP)</li> </ul>   |  |  |  |
|                        | PROFIBUS PA  |  |  |  |
|                        | Twisted, shielded two-wire c   | able. Cable type A is recommended .  |  |  |
|                        | For further information  | on planning and installing PROFIBUS PA networks see:   |  |  |
|                        | <ul> <li>Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning"<br/>(BA00034S)</li> <li>PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"</li> <li>IEC 61158-2 (MBP)</li> </ul>  |  |  |  |
| Overvoltage protection |  | ith integrated overvoltage protection for diverse approvals:<br>unted", option NA "Overvoltage protection" |  |  |
|                        | Input voltage range  | Values correspond to supply voltage specifications <sup>1)</sup>   |  |  |
|                        | Resistance per channel   | 2 · 0.5 Ω max  |  |  |
|                        | DC sparkover voltage   | 400 to 700 V   |  |  |
|                        | Trip surge voltage   | < 800 V  |  |  |
|                        | Capacitance at 1 MHz   | < 1.5 pF   |  |  |

| Nominal discharge current<br>(8/20 µs) | 10 kA                          |
|--|--------------------------------|
| Temperature range                      | -40 to +85 °C (-40 to +185 °F) |

1) The voltage is reduced by the amount of the internal resistance  $I_{min} \cdot R_i$ 

Depending on the temperature class, restrictions apply to the ambient temperature for device versions with overvoltage protection

## **Performance characteristics**

| Reference operating conditions | <ul> <li>Error limits based on ISO 11631</li> <li>Water with +15 to +45 °C (+59 to +113 °F) at2 to 6 bar (29 to 87 psi)</li> <li>Specifications as per calibration protocol</li> <li>Accuracy based on accredited calibration rigs that are traced to ISO 17025.</li> </ul> |  |  |  |  |
|--------------------------------|---|--|--|--|--|
|                                | To obtain measured errors, ע  | use the Applicator sizing tool $\rightarrow \square$ | 980  |  |  |
| Maximum measured error         | o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$  | l; T = medium temperature                            |  |  |  |
|                                | Base accuracy   |  |  |  |  |
|                                | Design fundamentals → 🗎 31  |  |  |  |  |
|                                | Mass flow and volume flow (liquids)   |  |  |  |  |
|                                | ±0.10 % o.r.  |  |  |  |  |
|                                | Mass flow (gases)   |  |  |  |  |
|                                | ±0.25 % o.r.  |  |  |  |  |
|                                | Density (liquids)   |  |  |  |  |
|                                | Under reference conditions  | Standard density calibration                         | Wide-range<br>Density specification <sup>1) 2)</sup> |  |  |
|                                | [g/cm³]   | [g/cm <sup>3</sup> ]                                 | [g/cm <sup>3</sup> ]                                 |  |  |
|                                | ±0.0005   | ±0.0005  | ±0.001   |  |  |

Order code for "Application package", option EE "Special density"

## Temperature

 $\pm 0.5\ ^\circ C\ \pm\ 0.005\ \cdot\ T\ ^\circ C\ (\pm 0.9\ ^\circ F\ \pm\ 0.003\ \cdot\ (T\ -\ 32)\ ^\circ F)$ 

## Zero point stability

| DN   |      | Zero point stability |          |
|------|------|----------------------|----------|
| [mm] | [in] | [kg/h]               | [lb/min] |
| 8    | 3⁄8  | 0.180                | 0.007    |
| 15   | 1/2  | 0.585                | 0.021    |
| 25   | 1    | 1.62                 | 0.059    |
| 40   | 1½   | 4.05                 | 0.149    |

| DN   |      | Zero point stability |          |  |
|------|------|----------------------|----------|--|
| [mm] | [in] | [kg/h]               | [lb/min] |  |
| 50   | 2    | 6.30                 | 0.231    |  |
| 80   | 3    | 16.2                 | 0.617    |  |

## **Flow values**

Flow values as turndown parameter depending on nominal diameter.

## SI units

| DN   | 1:1    | 1:10   | 1:20   | 1:50   | 1:100  | 1:500  |
|------|--------|--------|--------|--------|--------|--------|
| [mm] | [kg/h] | [kg/h] | [kg/h] | [kg/h] | [kg/h] | [kg/h] |
| 8    | 2 000  | 200    | 100    | 40     | 20     | 4      |
| 15   | 6500   | 650    | 325    | 130    | 65     | 13     |
| 25   | 18000  | 1800   | 900    | 360    | 180    | 36     |
| 40   | 45000  | 4500   | 2250   | 900    | 450    | 90     |
| 50   | 70000  | 7 000  | 3 500  | 1400   | 700    | 140    |
| 80   | 180000 | 18000  | 9000   | 3600   | 1800   | 360    |

## US units

| DN     | 1:1      | 1:10     | 1:20     | 1:50     | 1:100    | 1:500    |
|--------|----------|----------|----------|----------|----------|----------|
| [inch] | [lb/min] | [lb/min] | [lb/min] | [lb/min] | [lb/min] | [lb/min] |
| 3/8    | 73.50    | 7.350    | 3.675    | 1.470    | 0.735    | 0.147    |
| 1/2    | 238.9    | 23.89    | 11.95    | 4.778    | 2.389    | 0.478    |
| 1      | 661.5    | 66.15    | 33.08    | 13.23    | 6.615    | 1.323    |
| 1½     | 1654     | 165.4    | 82.70    | 33.08    | 16.54    | 3.308    |
| 2      | 2573     | 257.3    | 128.7    | 51.46    | 25.73    | 5.146    |
| 3      | 6615     | 661.5    | 330.8    | 132.3    | 66.15    | 13.23    |

## Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

| Accuracy | ±10 µA |
|----------|--------|
|----------|--------|

Pulse/frequency output

o.r. = of reading

| Accuracy | Max. ±100 ppm o.r. |
|----------|--------------------|
|----------|--------------------|


## Repeatability

## o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$ ; T = medium temperature

## Base repeatability

Design fundamentals  $\rightarrow \cong 31$ 

|                      | Mass flow and volume flow   | (liquids)  |  |  |  |
|----------------------|---|--|--|--|--|
|                      | ±0.05 % o.r.  |  |  |  |  |
|                      | Mass flow (gases)   |  |  |  |  |
|                      | ±0.20 % o.r.  |  |  |  |  |
|                      | Density (liquids)   |  |  |  |  |
|                      | $\pm 0.00025 \text{ g/cm}^3$  |  |  |  |  |
|                      | Temperature   |  |  |  |  |
|                      | ±0.25 °C ± 0.0025 · T °C (±   | 0.45 °F ± 0.0015 · (T−32) °F)  |  |  |  |
| Response time        |   | ads on the configuration (damping). On the measured variable: After 500 ms $\rightarrow$ 95 % of |  |  |  |
| Influence of ambient | Current output  |  |  |  |  |
| temperature          | o.r. = of reading   |  |  |  |  |
|                      | Additional error, in relation to the span of 16 mA:   |  |  |  |  |
|                      | Temperature coefficient at zero point (4 mA)  | 0.02 %/10 K  |  |  |  |
|                      | Temperature coefficient with span (20 mA)   | 0.05 %/10 K  |  |  |  |
|                      | <b>Pulse/frequency output</b><br>o.r. = of reading  |  |  |  |  |
|                      | Temperature coefficient   | Max. ±100 ppm o.r.   |  |  |  |
| Influence of medium  | Mass flow and volume flo  | W  |  |  |  |
| temperature          | o.f.s. = of full scale value  |  |  |  |  |
|                      | When there is a difference between the temperature for zero point adjustment and the process temperature, the additional measured error of the sensor is typically $\pm 0.0002 \%$ o.f.s./°C ( $\pm 0.0001 \%$ o. f.s./°F).   |  |  |  |  |
|                      | The effect is reduced if zero point adjustment is performed at process temperature.   |  |  |  |  |
|                      | <b>Density</b><br>When there is a difference between the density calibration temperature and the process temperature, the typical measured error of the sensor is $\pm 0.00005 \text{ g/cm}^3 /^{\circ}\text{C} (\pm 0.000025 \text{ g/cm}^3 /^{\circ}\text{F})$ . Field density calibration is possible. |  |  |  |  |
|                      | Wide-range density specification (special density calibration)<br>If the process temperature is outside the valid range ( $\rightarrow \cong 28$ ) the measured error is ±0.00005 g/cm <sup>3</sup> /°C (±0.000025 g/cm <sup>3</sup> /°F)   |  |  |  |  |



- 1 Field density calibration, for example at +20  $^{\circ}$ C (+68  $^{\circ}$ F)
- 2 Special density calibration

#### Temperature

±0.005 · T °C (± 0.005 · (T – 32) °F)

# Influence of medium pressure

The table below shows the effect on accuracy of mass flow due to a difference between calibration pressure and process pressure.

o.r. = of reading



- It is possible to compensate for the effect by:
- Reading in the current pressure measured value via the current input.
- Specifying a fixed value for the pressure in the device parameters.
- Operating Instructions → 🗎 81.

| DN   |      | [% o.r./bar]   | [% o.r./psi] |
|------|------|----------------|--------------|
| [mm] | [in] |                |              |
| 8    | 3/8  | no influence   |              |
| 15   | 1⁄2  | no influence   |              |
| 25   | 1    | no influence   |              |
| 40   | 1½   | -0.003 -0.0002 |              |
| 50   | 2    | -0.008 -0.0006 |              |
| 80   | 3    | -0.009 -0.0006 |              |

## Design fundamentals

o.r. = of reading, o.f.s. = of full scale value

BaseAccu = base accuracy in % o.r., BaseRepeat = base repeatability in % o.r.

MeasValue = measured value; ZeroPoint = zero point stability


#### Calculation of the maximum measured error as a function of the flow rate

| Flow rate   | Maximum measured error in % o.r.                          |
|---|---|
| $\geq \frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$ | ± BaseAccu  |
| < ZeroPoint<br>BaseAccu · 100                             | $\pm \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$ |
| A00213  | 33 A0021334   |

Calculation of the maximum repeatability as a function of the flow rate

| Flow rate   |          | Maximum repeatability in % o.r.   |
|---|----------|---|
| $\geq \frac{\frac{4}{3} \cdot \text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$ |          | ± ½ · BaseAccu  |
| A   | 40021341 |   |
| $< \frac{4/3 \cdot \text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$            |          | $\pm \frac{2}{3} \cdot \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$ |
| A A A A A A A A A A A A A A A A A A A                                       | A0021342 | A002134-  |

## Example for maximum measured error




*E* Maximum measured error in % o.r. (example)

*Q* Flow rate in % of maximum full scale value

## Installation

No special measures such as supports etc. are necessary. External forces are absorbed by the construction of the device.

## Mounting location




To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

#### Installation in down pipes

However, the following installation suggestion allows for installation in an open vertical pipeline. Pipe restrictions or the use of an orifice with a smaller cross-section than the nominal diameter prevent the sensor running empty while measurement is in progress.



■ 7 Installation in a down pipe (e.g. for batching applications)

1 Supply tank

2 Sensor

3 Orifice plate, pipe restriction

4 Valve

5 Batching tank

| D    | N    | Ø orifice plate, pipe restriction |      |  |
|------|------|-----------------------------------|------|--|
| [mm] | [in] | [mm]                              | [in] |  |
| 8    | 3⁄8  | 6                                 | 0.24 |  |
| 15   | 1/2  | 10                                | 0.40 |  |
| 25   | 1    | 14                                | 0.55 |  |
| 40   | 11/2 | 22                                | 0.87 |  |
| 50   | 2    | 28                                | 1.10 |  |
| 80   | 3    | 50                                | 1.97 |  |

## Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

|   | Orientatio                                    | Recommendation |  |
|---|---|----------------|--|
| A | Vertical orientation                          | A0015591       |  |
| В | Horizontal orientation, transmitter at top    | A0015589       | Exceptions:<br>$\rightarrow \textcircled{2}{8}, \textcircled{2}{34}$ |
| С | Horizontal orientation, transmitter at bottom | A0015590       | Exceptions:<br>$\rightarrow \mathbb{R}$ 8, $\cong$ 34                |
| D | Horizontal orientation, transmitter at side   | A0015592       | ×  |

1) Applications with low process temperatures may decrease the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.

2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.

|                           | Image: Second secon |                                |  |  |
|---------------------------|--|--------------------------------|--|--|
|                           | <ol> <li>Avoid this orientation for fluids with entrained solids: Risk of solids accumulating.</li> <li>Avoid this orientation for outgassing fluids: Risk of gas accumulating.</li> </ol>   |                                |  |  |
| Inlet and outlet runs     | No special precautions need to be taken for fittings which create turbulence, such as valves, elbows or T-pieces, as long as no cavitation occurs $\rightarrow \cong 42$ .   |                                |  |  |
| Special mounting          | Rupture disk   |                                |  |  |
| instructions              | Information that is relevant to the process: (Verweisziel existiert nicht, aber @y.link.required='true').  |                                |  |  |
|                           | The position of the rupture disk is indicated on a sticker beside it.  |                                |  |  |
|                           | The transportation guard must be removed.  |                                |  |  |
|                           | The existing connecting nozzles are not intended for the purpose of rinsing or pressure monitoring, but instead serve as the mounting location for the rupture disk.   |                                |  |  |
|                           | In the event of a failure of the rupture disk, a discharge device can be screwed onto the internal thread of the rupture disk in order to drain off any escaping medium.   |                                |  |  |
|                           | For information on the dimensions: see the "Mechanical construction -> Accessories" section  |                                |  |  |
|                           | Zero point adjustment  |                                |  |  |
|                           | All measuring devices are calibrated in accordance with state-of-the-art technology. Calibration takes place under reference conditions→ 🗎 28. Therefore, a zero point adjustment in the field is generally not required.  |                                |  |  |
|                           | <ul> <li>Experience shows that zero point adjustment is advisable only in special cases:</li> <li>To achieve maximum measuring accuracy even with low flow rates.</li> <li>Under extreme process or operating conditions (e.g. very high process temperatures or very high-viscosity fluids).</li> </ul>   |                                |  |  |
|                           | Environment  |                                |  |  |
| Ambient temperature range | Measuring device   | -40 to +60 °C (-40 to +140 °F) |  |  |

If a sensor is installed horizontally with a curved measuring tube, match the position of the sensor to the fluid properties.

-40 to +80 °C (-40 to +176 °F), preferably at +20 °C (+68 °F)

Avoid direct sunlight, particularly in warm climatic regions.

-20 to +60 °C (-4 to +140 °F)

temperature range.

You can order a weather protection cover from Endress+Hauser :  $\rightarrow \ \blacksquare 78$ 

The readability of the display may be impaired at temperatures outside the

Readability of the local display

► If operating outdoors:

1


Storage temperature


| Climate class                          | DIN EN 60068-2-38 (test Z/AD)   |  |  |
|--|---|--|--|
| Degree of protection                   | <b>Transmitter</b> <ul> <li>As standard: IP66/67, type 4X enclosure</li> <li>When housing is open: IP20, type 1 enclosure</li> <li>Display module: IP20, type 1 enclosure</li> </ul>  |  |  |
|  | <b>Sensor</b><br>IP66/67, type 4X enclosure   |  |  |
|  | <b>Connector</b><br>IP67, only in screwed situation   |  |  |
| Vibration resistance                   | <ul> <li>Vibration, sinusoidal according to IEC 60068-2-6</li> <li>2 to 8.4 Hz, 3.5 mm peak</li> <li>8.4 to 2 000 Hz, 1 g peak</li> <li>Vibration broad-band random, according to IEC 60068-2-64</li> <li>10 to 200 Hz, 0.003 g<sup>2</sup>/Hz</li> <li>200 to 2 000 Hz, 0.001 g<sup>2</sup>/Hz</li> <li>Total: 1.54 g rms</li> </ul>   |  |  |
| Shock resistance                       | Shock, half-sine according to IEC 60068-2-27<br>6 ms 30 g   |  |  |
| Impact resistance                      | Rough handling shocks according to IEC 60068-2-31   |  |  |
| Interior cleaning                      | <ul> <li>Cleaning in place (CIP)</li> <li>Sterilization in place (SIP)</li> <li>Options <ul> <li>Oil- and grease-free version for wetted parts, without inspection certificate Order code for "Service", option HA</li> <li>Oil- and grease-free version for wetted parts, with inspection certificate according to British Standard – BS IEC 60877:1999+ British Oxygen Cleaning – BOC degreasing specifications 00000-N-S-430-00-01</li> <li>Order code for "Service", option HB</li> </ul> </li> </ul> |  |  |
| Electromagnetic<br>compatibility (EMC) | As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) $$ For details, refer to the Declaration of Conformity.   |  |  |


# Process

| Medium temperature range     | 2  |                                 |   |  |
|------------------------------|--|---------------------------------|---|--|
|                              | Standard version   | –50 to +150 °C (–58 to +302 °F) | Order code for "Measuring tube<br>mat., wetted surface", option HA,<br>SA, SB, SC |  |
|                              | Extended temperature version   | -50 to +205 °C (-58 to +401 °F) | Order code for "Measuring tube<br>mat., wetted surface", option SD, SE,<br>SF, TH |  |
| Density                      | 0 to 2 000 kg/m $^3$ (0 to 125 lb/   | cf)                             |   |  |
| Pressure-temperature ratings | The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature. |                                 |   |  |
|                              | Pressure-temperature curves with temperature range +151 to +205 °C (+304 to +401 °F) exclusively for extended temperature version of measuring devices.  |                                 |   |  |


Flange according to EN 1092-1 (DIN 2501)








■ 10 With flange material 1.4404 (F316/F316L)




🖻 11 With flange material Alloy C22


### Flange JIS B2220




🖻 12 With flange material 1.4404 (F316/F316L), Alloy C22

### Flange DIN 11864-2 Form A





### Lap joint flange according to EN 1092-1 (DIN 2501)




🖻 14 With flange material 1.4301 (F304); wetted parts Alloy C22



### Lap joint flange according to ASME B16.5


🖻 15 With flange material 1.4301 (F304); wetted parts Alloy C22



# Lap joint flange JIS B2220

■ 16 With flange material 1.4301 (F304); wetted parts Alloy C22


### Thread DIN 11851



■ 17 With connection material 1.4404 (316/316L)


DIN 11851 allows for applications up to +140  $^{\circ}$ C (+284  $^{\circ}$ F) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

### Thread DIN 11864-1 Form A




■ 18 With connection material 1.4404 (316/316L)

### Thread ISO 2853




If With connection material 1.4404 (316/316L)

### Thread SMS 1145




SMS 1145 allows for applications up to 16 bar (232 psi) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

### VCO



☑ 20 With connection material 1.4404 (316/316L)



**Tri-Clamp** 

The clamp connections are suitable up to a maximum pressure of 16 bar (232 psi). Please observe the operating limits of the clamp and seal used as they can be over 16 bar (232 psi). The clamp and seal are not included in the scope of supply.

### Sensor housing

For standard versions with the temperature range -50 to +150 °C (-58 to +302 °F), the sensor housing is filled with dry nitrogen gas and protects the electronics and mechanics inside.

For all other temperature versions the sensor housing is filled with dry inert gas.

If a measuring tube fails (e.g. due to process characteristics like corrosive or abrasive fluids), the fluid will initially be contained by the sensor housing.

In the event of a tube failure, the pressure level inside the sensor housing will rise according to the operating process pressure. If the user judges that the sensor housing burst pressure does not provide an adequate safety margin, the device can be fitted with a rupture disk. This prevents excessively high pressure from forming inside the sensor housing. Therefore, the use of a rupture

disk is strongly recommended in applications involving high gas pressures, and particularly in applications in which the process pressure is greater than 2/3 of the sensor housing burst pressure.

If there is a need to drain the leaking medium into a discharge device, the sensor should be fitted with a rupture disk. Connect the discharge to the additional threaded connection  $\rightarrow \square 58$ .

If the sensor is to be purged with gas (gas detection), it should be equipped with purge connections.

Do not open the purge connections unless the containment can be filled immediately with a dry, inert gas. Use only low pressure to purge.

Maximum pressure:

- DN 08 to 150 (3/8 to 6"): 5 bar (72.5 psi)
- DN 250 (10"):
  - Medium temperature  $\leq$  100 °C (212 °F): 5 bar (72.5 psi)
  - Medium temperature > 100 °C (212 °F): 3 bar (43.5 psi)

### Burst pressure of the sensor housing

The following sensor housing burst pressures are only valid for standard devices and/or devices equipped with closed purge connections (not opened/as delivered).

If a device fitted with purge connections (order code for "Sensor option", option CH "Purge connection") is connected to the purge system, the maximum pressure is determined by the purge system itself or by the device, depending on which component has the lower pressure classification.

If the device is fitted with a rupture disk (order code for "Sensor option", option CA "Rupture disk"), the rupture disk trigger pressure is decisive .

The sensor housing burst pressure refers to a typical internal pressure which is reached prior to mechanical failure of the sensor housing and which was determined during type testing. The corresponding type test declaration can be ordered with the device (order code for "Additional approval", option LN "Sensor housing burst pressure, type test").

| D    | N    | Sensor housing burst pressure |       |  |  |
|------|------|-------------------------------|-------|--|--|
| [mm] | [in] | [bar]                         | [psi] |  |  |
| 8    | 3⁄8  | 400                           | 5800  |  |  |
| 15   | 1/2  | 350                           | 5070  |  |  |
| 25   | 1    | 280                           | 4060  |  |  |
| 40   | 11/2 | 260                           | 3770  |  |  |
| 50   | 2    | 180                           | 2610  |  |  |
| 80   | 3    | 120                           | 1740  |  |  |

For information on the dimensions: see the "Mechanical construction" section  $\rightarrow \square 44$ 

| Rupture disk | To increase the level of safety, a device version with a rupture disk with a trigger pressure of 10 to 15 bar (145 to 217.5 psi)can be used (order code for "Sensor option", option CA "rupture disk"). |  |  |  |  |  |
|--------------|---|--|--|--|--|--|
|              | The use of rupture disks cannot be combined with the separately available heating jacket.   |  |  |  |  |  |
|              | For information on the dimensions: see the "Mechanical construction" section (accessories) $\rightarrow$ 🗎 58   |  |  |  |  |  |
| Flow limit   | Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.  |  |  |  |  |  |
|              | For an overview of the full scale values for the measuring range, see the "Measuring range" section $\rightarrow \cong 8$   |  |  |  |  |  |


|                    | <ul> <li>The minimum recommended full scale value is approx. 1/20 of the maximum full scale value</li> <li>In most applications, 20 to 50 % of the maximum full scale value can be considered ideal</li> <li>A low full scale value must be selected for abrasive media (such as liquids with entrained solids): flow velocity &lt; 1 m/s (&lt; 3 ft/s).</li> <li>For gas measurement the following rules apply: <ul> <li>The flow velocity in the measuring tubes should not exceed half the sound velocity (0.5 Mach).</li> <li>The maximum mass flow depends on the density of the gas: formula → 🖺 8</li> </ul> </li> <li>To calculate the flow limit, use the <i>Applicator</i> sizing tool → 🖺 80</li> </ul>   |
|--------------------|--|
| Pressure loss      | To calculate the pressure loss, use the <i>Applicator</i> sizing tool $\rightarrow \boxtimes 80$<br>Promass F with reduced pressure loss: order code for "Sensor option", option CE "Reduced pressure loss"  |
| System pressure    | It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas.<br>This is prevented by means of a sufficiently high system pressure.<br>For this reason, the following mounting locations are recommended:<br>• At the lowest point in a vertical pipe<br>• Downstream from pumps (no danger of vacuum)   |
|                    |  |
| Thermal insulation | <ul> <li>In the case of some fluids, it is important to keep the heat radiated from the sensor to the transmitter to a low level. A wide range of materials can be used for the required insulation.</li> <li>The following device versions are recommended for versions with thermal insulation: Extended temperature version:</li> <li>Order code for "Measuring tube material", option SD, SE, SF or TH with an extended neck length of 105 mm (4.13 in).</li> <li><b>NOTICE</b></li> <li><b>Electronics overheating on account of thermal insulation!</b></li> <li>A Recommended orientation: horizontal orientation, transmitter housing pointing downwards.</li> <li>Do not insulate the transmitter housing.</li> <li>Maximum permissible temperature at the lower end of the transmitter housing: 80 °C (176 °F)</li> <li>Thermal insulation with extended neck free: We recommend that you do not insulate the extended neck in order to ensure optimum dissipation of heat.</li> </ul>   |
|                    | Image: Second secon |
| Heating            | Some fluids require suitable measures to avoid loss of heat at the sensor.<br>Heating options<br>• Electrical heating, e.g. with electric band heaters   |

- Electrical heating, e.g. with electric bar
  Via pipes carrying hot water or steam
  Via heating jackets

Heating jackets for the sensors can be ordered as accessories from Endress+Hauser.  $\rightarrow \square$  79


# NOTICE Danger of overheating when heating Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F). Ensure that sufficient convection takes place at the transmitter neck. Ensure that a sufficiently large area of the transmitter neck remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling. When using in potentially explosive atmospheres, observe the information in the device-specific Ex documentation. For detailed information on the temperature tables, see the separate document entitled "Safety Instructions" (XA) for the device. Vibrations The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by plant vibrations.

# Mechanical construction



### **Compact version**

Compact version



Dimensions for version without overvoltage protection

Order code for "Housing", options B "GT18 dual compartment, 316L", C "GT20 dual compartment aluminum coated"

| DN<br>[mm] | A <sup>1)</sup><br>[mm] | B <sup>1)</sup><br>[mm] | C<br>[mm] | D <sup>2)</sup><br>[mm] | E<br>[mm] | F <sup>2)</sup><br>[mm] | G<br>[mm] | H <sup>3)</sup><br>[mm] | I <sup>3)</sup><br>[mm] | K<br>[mm] | L<br>[mm] |
|------------|-------------------------|-------------------------|-----------|-------------------------|-----------|-------------------------|-----------|-------------------------|-------------------------|-----------|-----------|
| 8          | 162                     | 102                     | 60        | 165                     | 75        | 90                      | 5.35      | 268                     | 343                     | 75        | 4)        |
| 15         | 162                     | 102                     | 60        | 165                     | 75        | 90                      | 8.30      | 268                     | 343                     | 75        | 4)        |
| 25         | 162                     | 102                     | 60        | 165                     | 75        | 90                      | 12.0      | 268                     | 343                     | 75        | 4)        |
| 40         | 162                     | 102                     | 60        | 165                     | 75        | 90                      | 17.6      | 273                     | 378                     | 105       | 4)        |
| 50         | 162                     | 102                     | 60        | 165                     | 75        | 90                      | 26.0      | 283                     | 424                     | 141       | 4)        |
| 80         | 162                     | 102                     | 60        | 165                     | 75        | 90                      | 40.5      | 302                     | 502                     | 200       | 4)        |

1) For version without local display: values - 7 mm


For versions with overvoltage protection (OVP): values + 8 mm For version without local display: values - 3 mm 2)

3)

4) Dependent on the respective process connection

### Flange connections

Fixed flange EN 1092-1, ASME B16.5, JIS B2220



Length tolerance for dimension L in mm: +1.5 / -2.0

### Flange according to EN 1092-1 (DIN 2501): PN 40

1.4404 (F316/F316L): order code for "Process connection", option D2S Alloy C22: order code for "Process connection", option D2C

Flange with groove according to EN 1092-1 Form D (DIN 2512N): PN 40 1.4404 (F316/F316L): order code for "Process connection", option D6S Alloy C22: order code for "Process connection", option D6C

| DN<br>[mm]      | A<br>[mm]        | B<br>[mm]      | C<br>[mm]        | D<br>[mm]      | E<br>[mm]  | L<br>[mm]             |
|-----------------|------------------|----------------|------------------|----------------|------------|-----------------------|
| 8 <sup>1)</sup> | 95               | 65             | 4 × Ø14          | 16             | 17.3       | 370/510 <sup>2)</sup> |
| 15              | 95               | 65             | 4ר14             | 16             | 17.3       | 404/510 <sup>2)</sup> |
| 25              | 115              | 85             | 4ר14             | 18             | 28.5       | 440/600 <sup>2)</sup> |
| 40              | 150              | 110            | 4 × Ø18          | 18             | 43.1       | 550                   |
| 50              | 165              | 125            | 4 × Ø18          | 20             | 54.5       | 715/715 <sup>2)</sup> |
| 80              | 200              | 160            | 8 × Ø18          | 24             | 82.5       | 840/915 <sup>2)</sup> |
| Surface rough   | ness (flange): H | EN 1092-1 Fori | m B1 (DIN 2526 F | orm C), Ra 3.2 | to 12.5 µm | <u>.</u>              |

1) DN 8 with DN 15 flanges as standard

2) Installation length in accordance with NAMUR recommendation NE 132 optionally available (order code for "Process connection", option D2N or D6N (with groove))

| Flange according to EN 1092-1 (DIN 2501): PN 40 (with DN 25 flanges)<br>1.4404 (F316/F316L): order code for "Process connection", option R2S   |                  |                 |                   |                  |       |     |  |  |  |
|--|------------------|-----------------|-------------------|------------------|-------|-----|--|--|--|
| DN         A         B         C         D         E         L           [mm]         [mm]         [mm]         [mm]         [mm]         [mm] |                  |                 |                   |                  |       |     |  |  |  |
| 8  | 115              | 85              | 4 × Ø14           | 18               | 28.5  | 440 |  |  |  |
| 15 115 85 4ר14 18 28.5 440   |                  |                 |                   |                  |       |     |  |  |  |
| Surface rough  | ess (flange). EN | [ 1092-1 Form F | 31 (DIN 2526 Form | (1) Ra 3.2 to 1' | 25.um |     |  |  |  |

Surface roughness (flange): EN 1092-1 Form B1 (DIN 2526 Form C), Ra 3.2 to 12.5  $\mu$ m

| Flange according to EN 1092-1 (DIN 2501): PN 40 with reduction in nominal diameter 1.4404 (F316/F316L)  |                 |                    |           |          |                  |       |       |          |  |  |
|---|-----------------|--------------------|-----------|----------|------------------|-------|-------|----------|--|--|
| DN<br>[mm]reduction<br>to DN<br>[mm]Order code for<br>"ProcessABCDEL[mm]to DN<br>[mm]"Process<br>connection",<br>option[mm][mm][mm][mm][mm][mm] |                 |                    |           |          |                  |       |       |          |  |  |
| 50  | 40              | DFS                | 165       | 125      | 4ר18             | 20    | 54.5  | 555      |  |  |
| 80  | 50              | DGS                | 200       | 160      | 8ר18             | 24    | 82.5  | 840      |  |  |
| 100   | 80              | DIS                | 235       | 190      | 8 × Ø22          | 24    | 107.1 | 874      |  |  |
| Surface ro  | oughness (flang | e): EN 1092-1 Form | B1 (DIN 2 | 526 Form | C), Ra 3.2 to 12 | .5 µm |       | <u>.</u> |  |  |

### Flange according to EN 1092-1 (DIN 2501): PN 63

1.4404 (F316/F316L): order code for "Process connection", option D3S Alloy C22: order code for "Process connection", option D3C

### Flange with groove according to EN 1092-1 Form D (DIN 2512N): PN 63

1.4404 (F316/F316L): order code for "Process connection", option D7S Alloy C22: order code for "Process connection", option D7C

Anoy CZZ. order code for Process connection, option DrC

| DN<br>[mm] | A<br>[mm] | B<br>[mm] | C<br>[mm] | D<br>[mm] | E<br>[mm] | L<br>[mm] |
|------------|-----------|-----------|-----------|-----------|-----------|-----------|
| 50         | 180       | 135       | 4 × Ø22   | 26        | 54.5      | 724       |
| 80         | 215       | 170       | 8 × Ø22   | 28        | 81.7      | 875       |

Surface roughness (flange):

EN 1092-1 Form B1 (DIN 2526 Form C), Ra 3.2 to 12.5  $\mu m$  EN 1092-1 Form B2 (DIN 2526 Form E), Ra 0.8 to 3.2  $\mu m$ 

### Flange according to EN 1092-1 (DIN 2501): PN 100

1.4404 (F316/F316L): order code for "Process connection", option D4S Alloy C22: order code for "Process connection", option D4C

### Flange with groove according to EN 1092-1 Form D (DIN 2512N): PN 100 1.4404 (F316/F316L): order code for "Process connection", option D8S

Alloy C22: order code for "Process connection", option D8C

| DN<br>[mm]      | A<br>[mm]         | B<br>[mm]     | C<br>[mm]         | D<br>[mm]          | E<br>[mm] | L<br>[mm] |
|-----------------|-------------------|---------------|-------------------|--------------------|-----------|-----------|
| 8 <sup>1)</sup> | 105               | 75            | 4ר14              | 20                 | 17.3      | 400       |
| 15              | 105               | 75            | 4ר14              | 20                 | 17.3      | 420       |
| 25              | 140               | 100           | 4 × Ø18           | 24                 | 28.5      | 470       |
| 40              | 170               | 125           | 4 × Ø22           | 26                 | 42.5      | 590       |
| 50              | 195               | 145           | 4 × Ø26           | 28                 | 53.9      | 740       |
| 80              | 230               | 180           | 8 × Ø26           | 32                 | 80.9      | 885       |
| Surface roughn  | iess (flange): EN | 1092-1 Form H | 32 (DIN 2526 Form | n E), Ra 0.8 to 3. | 2 µm      |           |

1) DN 8 with DN 15 flanges as standard

| Flange according to ASME B16.5: Class 150<br>1.4404 (F316/F316L): order code for "Process connection", option AAS<br>Alloy C22: order code for "Process connection", option AAC |     |      |           |      |      |     |  |  |  |
|---|-----|------|-----------|------|------|-----|--|--|--|
| DN         A         B         C         D         E         L           [mm]         [mm]         [mm]         [mm]         [mm]         [mm]                                  |     |      |           |      |      |     |  |  |  |
| 8 <sup>1)</sup>   | 90  | 60.3 | 4 × Ø15.7 | 11.2 | 15.7 | 370 |  |  |  |
| 15  | 90  | 60.3 | 4 × Ø15.7 | 11.2 | 15.7 | 404 |  |  |  |
| 25  | 110 | 79.4 | 4 × Ø15.7 | 14.2 | 26.7 | 440 |  |  |  |

### Flange according to ASME B16.5: Class 150 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC

| DN<br>[mm]    | A<br>[mm]        | B<br>[mm]            | C<br>[mm] | D<br>[mm] | E<br>[mm] | L<br>[mm] |
|---------------|------------------|----------------------|-----------|-----------|-----------|-----------|
| 40            | 125              | 98.4                 | 4 × Ø15.9 | 15.9      | 40.9      | 550       |
| 50            | 150              | 120.7                | 4 × Ø19.1 | 19.1      | 52.6      | 715       |
| 80            | 190              | 152.4                | 4 × Ø19.1 | 23.9      | 78.0      | 840       |
| Surface rough | ness (flange). B | -<br>a 3 2 to 6 3 um |           |           |           |           |

Surface roughness (flange): Ra 3.2 to 6.3  $\mu$ m

1) DN 8 with DN 15 flanges as standard

Flange according to ASME B16.5: Class 150 with reduction in nominal diameter 1.4404 (F316/F316L)

| DN<br>[mm] | reduction<br>to DN<br>[mm] | Order code for<br>"Process<br>connection",<br>option | A<br>[mm] | B<br>[mm] | C<br>[mm] | D<br>[mm] | E<br>[mm] | L<br>[mm] |  |  |  |  |
|------------|----------------------------|--|-----------|-----------|-----------|-----------|-----------|-----------|--|--|--|--|
| 50         | 40                         | AHS  | 150       | 120.7     | 4 × Ø19.1 | 19.1      | 52.6      | 550       |  |  |  |  |
| 80         | 50                         | AJS  | 190       | 152.4     | 4ר19.1    | 23.9      | 78.0      | 720       |  |  |  |  |
| 100        | 80                         | ALS  | 230       | 190.5     | 8ר19.1    | 23.9      | 102.4     | 874       |  |  |  |  |
| Surfacer   | oughnoss (flong            | a), Do 2 2 to 6 2 um                                 |           |           |           |           |           |           |  |  |  |  |

Surface roughness (flange): Ra 3.2 to 6.3  $\mu$ m

### Flange according to ASME B16.5: Class 300 1.4404 (F316/F316L): order code for "Process connection", option ABS Alloy C22: order code for "Process connection", option ABC В С D Ε DN Α L [mm] [mm] [mm] [mm] [mm] [mm] [mm] 8<sup>1)</sup> 95 4 × Ø15.7 370 66.7 14.2 15.7 15 95 66.7 4 × Ø15.7 14.2 15.7 404 25 125 88.9 4ר19.1 17.5 26.7 440 40 155 114.3 4ר22.3 20.6 40.9 550 50 165 127 8ר19.1 22.3 52.6 715 80 210 168.3 8ר22.3 28.4 78.0 840 Surface roughness (flange): Ra 3.2 to 6.3 µm

1) DN 8 with DN 15 flanges as standard

Flange according to ASME B16.5: Class 300 with reduction in nominal diameter 1.4404 (F316/F316L)

| 1.4404 (   | F210/F210L)                |  |           |           |           |           |           |           |
|------------|----------------------------|--|-----------|-----------|-----------|-----------|-----------|-----------|
| DN<br>[mm] | reduction<br>to DN<br>[mm] | Order code for<br>"Process<br>connection",<br>option | A<br>[mm] | B<br>[mm] | C<br>[mm] | D<br>[mm] | E<br>[mm] | L<br>[mm] |
| 50         | 40                         | AIS  | 165       | 127       | 8ר19.1    | 22.3      | 52.6      | 615       |
| 80         | 50                         | AKS  | 210       | 168.3     | 8 × Ø22.3 | 28.4      | 78.0      | 732       |
| 100        | 80                         | AMS  | 255       | 200       | 8 × Ø22.3 | 31.7      | 102.4     | 894       |
| Surface r  | oughness (flang            | je): Ra 3.2 to 6.3 μm                                |           |           |           | -         |           |           |

### Flange according to ASME B16.5: Class 600

1.4404 (F316/F316L): order code for "Process connection", option ACS

Alloy C22: order code for "Process connection", option ACC

|                 | ter coue jor 170 | cebb connection | , option nee |           |           |           |
|-----------------|------------------|-----------------|--------------|-----------|-----------|-----------|
| DN<br>[mm]      | A<br>[mm]        | B<br>[mm]       | C<br>[mm]    | D<br>[mm] | E<br>[mm] | L<br>[mm] |
| 8 <sup>1)</sup> | 95               | 66.7            | 4 × Ø15.7    | 20.6      | 13.9      | 400       |
| 15              | 95               | 66.7            | 4 × Ø15.7    | 20.6      | 13.9      | 420       |
| 25              | 125              | 88.9            | 4 × Ø19.1    | 23.9      | 24.3      | 490       |
| 40              | 155              | 114.3           | 4 × Ø22.3    | 28.7      | 38.1      | 600       |
| 50              | 165              | 127             | 8 × Ø19.1    | 31.8      | 49.2      | 742       |
| 80              | 210              | 168.3           | 8 × Ø22.3    | 38.2      | 73.7      | 900       |
| Surface rough   | ness (flange): R | a 3.2 to 6.3 μm |              |           |           |           |

1) DN 8 with DN 15 flanges as standard

### Flange JIS B2220: 10K

| 1.4404 (F316/F316L): order code for "Process connection", option NDS |
|--|
| Alloy C22: order code for "Process connection", option NDC           |

| DN<br>[mm]    | A<br>[mm]          | B<br>[mm]     | C<br>[mm] | D<br>[mm] | E<br>[mm] | L<br>[mm] |
|---------------|--------------------|---------------|-----------|-----------|-----------|-----------|
| 50            | 155                | 120           | 4 × Ø19   | 16        | 50        | 715       |
| 80            | 185                | 150           | 8 × Ø19   | 18        | 80        | 832       |
| Surface rough | Less (flange) · Ra | 3 2 to 6 3 um |           |           |           |           |

Surface roughness (flange): Ra 3.2 to 6.3  $\mu$ m

### Flange JIS B2220: 20K

### 1.4404 (F316/F316L): order code for "Process connection", option NES

Alloy C22: order code for "Process connection", option NEC

| ,               | · · · · · · · · · · · · · · · · · · · | ,             |           |           |           |           |
|-----------------|---------------------------------------|---------------|-----------|-----------|-----------|-----------|
| DN<br>[mm]      | A<br>[mm]                             | B<br>[mm]     | C<br>[mm] | D<br>[mm] | E<br>[mm] | L<br>[mm] |
| 8 <sup>1)</sup> | 95                                    | 70            | 4 × Ø15   | 14        | 15        | 370       |
| 15              | 95                                    | 70            | 4 × Ø15   | 14        | 15        | 404       |
| 25              | 125                                   | 90            | 4 × Ø19   | 16        | 25        | 440       |
| 40              | 140                                   | 105           | 4 × Ø19   | 18        | 40        | 550       |
| 50              | 155                                   | 120           | 8 × Ø19   | 18        | 50        | 715       |
| 80              | 200                                   | 160           | 8 × Ø23   | 22        | 80        | 832       |
| Surface roughr  | ness (flange): Ra                     | 1.6 to 3.2 µm |           |           |           |           |

1) DN 8 with DN 15 flanges as standard

|                 |           |           | connection", option<br>option <b>NGC</b> | NGS       |           |           |
|-----------------|-----------|-----------|--|-----------|-----------|-----------|
| DN<br>[mm]      | A<br>[mm] | B<br>[mm] | C<br>[mm]                                | D<br>[mm] | E<br>[mm] | L<br>[mm] |
| 8 <sup>1)</sup> | 115       | 80        | 4 × Ø19                                  | 20        | 15        | 400       |
| 15              | 115       | 80        | 4 × Ø19                                  | 20        | 15        | 425       |
| 25              | 130       | 95        | 4 × Ø19                                  | 22        | 25        | 485       |
| 40              | 160       | 120       | 4 × Ø23                                  | 24        | 38        | 600       |
| 50              | 165       | 130       | 8 × Ø19                                  | 26        | 50        | 760       |

|            | <b>/F316L):</b> order a<br>ler code for "Proc |           | connection", option<br>option <b>NGC</b> | NGS       |           |          |
|------------|---|-----------|--|-----------|-----------|----------|
| DN<br>[mm] | A<br>[mm]                                     | B<br>[mm] | C<br>[mm]                                | D<br>[mm] | E<br>[mm] | L<br>[mm |
| 80         | 210   | 170       | 8 × Ø23                                  | 32        | 75        | 890      |


DN 8 with DN 15 flanges as standard 1)


Flange JIS B2220: 63K 1.4404 (F316/F316L): order code for "Process connection", option NHS Alloy C22: order code for "Process connection", option NHC

|                 | e. couc jo. 1.oc  |               | option    |           |           |           |
|-----------------|-------------------|---------------|-----------|-----------|-----------|-----------|
| DN<br>[mm]      | A<br>[mm]         | B<br>[mm]     | C<br>[mm] | D<br>[mm] | E<br>[mm] | L<br>[mm] |
| 8 <sup>1)</sup> | 120               | 85            | 4 × Ø19   | 23        | 12        | 420       |
| 15              | 120               | 85            | 4 × Ø19   | 23        | 12        | 440       |
| 25              | 140               | 100           | 4 × Ø23   | 27        | 22        | 494       |
| 40              | 175               | 130           | 4 × Ø25   | 32        | 35        | 620       |
| 50              | 185               | 145           | 8 × Ø23   | 34        | 48        | 775       |
| 80              | 230               | 185           | 8 × Ø25   | 40        | 73        | 915       |
| Surface roughr  | iess (flange): Ra | 1.6 to 3.2 µm |           | ·         |           | ×         |

1) DN 8 with DN 15 flanges as standard

### Fixed flange DIN 11864-2





Length tolerance for dimension L in mm: +1.5 / -2.0


# Flange DIN11864-2 Form A, for pipe according to DIN11866 series A, flat with notch 1.4404 (316/316L)


Order code for "Process connection", option KCS

| DN<br>[mm] | A<br>[mm] | B<br>[mm] | C<br>[mm]             | D<br>[mm] | E<br>[mm] | L<br>[mm] |  |  |  |
|------------|-----------|-----------|-----------------------|-----------|-----------|-----------|--|--|--|
| 8          | 54        | 37        | 4 × Ø9                | 10        | 10        | 387       |  |  |  |
| 15         | 59        | 42        | 4 × Ø9                | 10        | 16        | 418       |  |  |  |
| 25         | 70        | 53        | 4 × Ø9                | 10        | 26        | 454       |  |  |  |
| 40         | 82        | 65        | 4 × Ø9                | 10        | 38        | 560       |  |  |  |
| 50         | 94        | 77        | 4 × Ø9                | 10        | 50        | 720       |  |  |  |
| 80         | 133       | 112       | 8ר11                  | 12        | 81        | 900       |  |  |  |
|            |           |           | l approval", option l | 5         | n with    | 1         |  |  |  |

 $Ra_{max} = 0.76 \ \mu m$ : order code for "Measuring tube material", option SB, SE or

 $Ra_{max} = 0.38 \ \mu m$ : order code for "Measuring tube material", option SC, SF  $Ra_{max} = 0.38 \ \mu m$  electropolished: order code for "Measuring tube material", option BC





Length tolerance for dimension L in mm: +1.5 / -2.0

| .4301 (F        | 304), wetted | l parts Alloy | <b>1092-1 Form D:</b> 1<br>C22<br>option <b>DAC</b> | PN 40     |           |           |           |   |
|-----------------|--------------|---------------|---|-----------|-----------|-----------|-----------|---|
| DN<br>[mm]      | A<br>[mm]    | B<br>[mm]     | C<br>[mm]   | D<br>[mm] | E<br>[mm] | F<br>[mm] | L<br>[mm] | L <sub>diff</sub> <sup>1)</sup><br>[mm] |
| 8 <sup>2)</sup> | 95           | 65            | $4 \times Ø14$                                      | 14.5      | 45        | 17.3      | 370       | 0                                       |
| 15              | 95           | 65            | $4 \times Ø14$                                      | 14.5      | 45        | 17.3      | 404       | 0                                       |
| 25              | 115          | 85            | $4 \times Ø14$                                      | 16.5      | 68        | 28.5      | 444       | +4                                      |
| 40              | 150          | 110           | $4 \times Ø18$                                      | 21        | 88        | 43.1      | 560       | +10                                     |
| 50              | 165          | 125           | $4 \times Ø18$                                      | 23        | 102       | 54.5      | 719       | +4                                      |
| 80              | 200          | 160           | 8 × Ø18   | 29        | 138       | 82.5      | 848       | +8                                      |

1) Difference to installation length of the welding neck flange (order code for "Process connection", option D2C)

2) DN 8 with DN 15 flanges as standard

| ruer coue       | e for "Process | connection", | , option <b>ADC</b> |           |           |           |           |   |
|-----------------|----------------|--------------|---------------------|-----------|-----------|-----------|-----------|---|
| DN<br>[mm]      | A<br>[mm]      | B<br>[mm]    | C<br>[mm]           | D<br>[mm] | E<br>[mm] | F<br>[mm] | L<br>[mm] | L <sub>diff</sub> <sup>1)</sup><br>[mm] |
| 8 <sup>2)</sup> | 90             | 60.3         | 4 × Ø 15.7          | 15        | 35.1      | 15.7      | 370       | 0                                       |
| 15              | 90             | 60.3         | 4 × Ø 15.7          | 15        | 35.1      | 15.7      | 404       | 0                                       |
| 25              | 110            | 79.4         | 4 × Ø 15.7          | 16        | 50.8      | 26.7      | 440       | 0                                       |
| 40              | 125            | 98.4         | 4 × Ø 15.7          | 15.9      | 73.2      | 40.9      | 550       | 0                                       |
| 50              | 150            | 120.7        | 4 × Ø 19.1          | 19        | 91.9      | 52.6      | 715       | 0                                       |
| 80              | 190            | 152.4        | 4 × Ø 19.1          | 22.3      | 127.0     | 78.0      | 840       | 0                                       |

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC)

2) DN 8 with DN 15 flanges as standard

| •               | •/        | l parts Alloy<br>connection", | option AEC |           |           |           |           |   |
|-----------------|-----------|-------------------------------|------------|-----------|-----------|-----------|-----------|---|
| DN<br>[mm]      | A<br>[mm] | B<br>[mm]                     | C<br>[mm]  | D<br>[mm] | E<br>[mm] | F<br>[mm] | L<br>[mm] | L <sub>diff</sub> <sup>1)</sup><br>[mm] |
| 8 <sup>2)</sup> | 95        | 66.7                          | 4 × Ø 15.7 | 16.5      | 35.1      | 15.7      | 376       | +6                                      |
| 15              | 95        | 66.7                          | 4 × Ø 15.7 | 16.5      | 35.1      | 15.7      | 406       | +2                                      |
| 25              | 125       | 88.9                          | 4 × Ø 19.1 | 21.0      | 50.8      | 26.7      | 450       | +10                                     |
| 40              | 155       | 114.3                         | 4 × Ø 22.3 | 23.0      | 73.2      | 40.9      | 564       | +14                                     |
| 50              | 165       | 127                           | 8 × Ø 19.1 | 25.5      | 91.9      | 52.6      | 717       | +2                                      |
| 80              | 210       | 168.3                         | 8 × Ø 22.3 | 31.0      | 127.0     | 78.0      | 852.6     | +12.6                                   |

1) Difference to installation length of the welding neck flange (order code for "Process connection", option ABC)

2) DN 8 with DN 15 flanges as standard

| Lap joint flange according to ASME B16.5: Class 600<br>1.4301 (F304), wetted parts Alloy C22<br>Order code for "Process connection", option AFC |   |           |                                |           |           |           |           |   |  |  |
|---|---|-----------|--------------------------------|-----------|-----------|-----------|-----------|---|--|--|
| DN<br>[mm]  | A<br>[mm]                                     | B<br>[mm] | C<br>[mm]                      | D<br>[mm] | E<br>[mm] | F<br>[mm] | L<br>[mm] | L <sub>diff</sub> <sup>1)</sup><br>[mm] |  |  |
| 8 <sup>2)</sup>   | 95  | 66.7      | 4 × Ø 15.7                     | 17.0      | 35.1      | 13.9      | 400       | 0                                       |  |  |
| 15  | 95  | 66.7      | 4 × Ø 15.7                     | 17.0      | 35.1      | 13.9      | 420       | 0                                       |  |  |
| 25  | 125   | 88.9      | 4 × Ø 19.1                     | 21.5      | 50.8      | 24.3      | 490       | 0                                       |  |  |
| 40  | 155   | 114.3     | 4 × Ø 22.3                     | 25.0      | 73.2      | 38.1      | 600       | 0                                       |  |  |
| 50  | 165   | 127       | 8 × Ø 19.1                     | 28.0      | 91.9      | 49.2      | 742       | 0                                       |  |  |
| 80  | 210   | 168.3     | 8 × Ø 22.3 35.0 127.0 73.7 900 |           |           |           |           |   |  |  |
| Surface rou   | Surface roughness (flange): Ra 3.2 to 12.5 µm |           |                                |           |           |           |           |   |  |  |

1) Difference to installation length of the welding neck flange (order code for "Process connection", option ACC)

2) DN 8 with DN 15 flanges as standard


| 1.4301 (F3                                    | Lap joint flange JIS B2220: 20K<br>1.4301 (F304), wetted parts Alloy C22<br>Order code for "Process connection", option NIC |           |           |           |           |           |           |   |  |  |
|---|---|-----------|-----------|-----------|-----------|-----------|-----------|---|--|--|
| DN<br>[mm]                                    | A<br>[mm]   | B<br>[mm] | C<br>[mm] | D<br>[mm] | E<br>[mm] | F<br>[mm] | L<br>[mm] | L <sub>diff</sub> <sup>1)</sup><br>[mm] |  |  |
| 8 <sup>2)</sup>                               | 95  | 70        | 4 × Ø 15  | 14        | 51        | 15        | 370       | 0                                       |  |  |
| 15  | 95  | 70        | 4 × Ø 15  | 14        | 51        | 15        | 404       | 0                                       |  |  |
| 25  | 125   | 90        | 4 × Ø 19  | 18.5      | 67        | 25        | 440       | 0                                       |  |  |
| 40  | 140   | 105       | 4 × Ø 19  | 18.5      | 81        | 40        | 550       | 0                                       |  |  |
| 50  | 155   | 120       | 8ר19      | 23        | 96        | 50        | 715       | 0                                       |  |  |
| 80  | 200   | 160       | 8 × Ø 23  | 29        | 132       | 80        | 844       | +12                                     |  |  |
| Surface roughness (flange): Ra 3.2 to 12.5 μm |   |           |           |           |           |           |           |   |  |  |

1) Difference to installation length of the welding neck flange (order code for "Process connection", option NEC)

2) DN 8 with DN 15 flanges as standard

### **Clamp connections**

Tri-Clamp



Length tolerance for dimension L in mm: +1.5 / -2.0

| Tri-Clamp (¼"), for pipe according to DIN 11866 series C<br>1.4404 (316/316L)<br>Order code for "Process connection", option FDW |               |           |           |           |  |  |  |
|--|---------------|-----------|-----------|-----------|--|--|--|
| DN<br>[mm]   | Clamp<br>[in] | A<br>[mm] | B<br>[mm] | L<br>[mm] |  |  |  |
| 8  | 1/2           | 25.0      | 9.5       | 367       |  |  |  |
| 15   | 1⁄2           | 25.0      | 9.5       | 398       |  |  |  |

3-A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max}$  = 0.76  $\mu m$ : order code for "Measuring tube material", option SB, SE or

 $Ra_{max}^{\rm max}$  = 0.38  $\mu m$ : order code for "Measuring tube material", option SC, SF

 $Ra_{max} = 0.38 \ \mu m$  electropolished: order code for "Measuring tube material", option BC

# Tri-Clamp ( $\geq$ 1"), for pipe according to DIN 11866 series C 1.4404 (316/316L)

Order code for "Process connection", option FTS

| DN<br>[mm] | Clamp<br>[in] | A<br>[mm] | B<br>[mm] | L<br>[mm] |
|------------|---------------|-----------|-----------|-----------|
| 8          | 1             | 50.4      | 22.1      | 367       |
| 15         | 1             | 50.4      | 22.1      | 398       |
| 25         | 1             | 50.4      | 22.1      | 434       |
| 40         | 11⁄2          | 50.4      | 34.8      | 560       |
| 50         | 2             | 63.9      | 47.5      | 720       |
| 80         | 3             | 90.9      | 72.9      | 900       |

3-A version available: order code for "Additional approval", option LP in conjunction with


 $Ra_{max}$  = 0.76  $\mu m$ : order code for "Measuring tube material", option SB, SE or

 $Ra_{max} = 0.38 \ \mu m$ : order code for "Measuring tube material", option SC, SF

 $Ra_{max} = 0.38 \ \mu m$  electropolished: order code for "Measuring tube material", option BC

### Threaded couplings

Thread DIN 11851, DIN11864-1, SMS 1145





Length tolerance for dimension L in mm: +1.5 / -2.0

| Thread DIN 11851, for pipe according to DIN11866, series A<br>1.4404 (316/316L)<br>Order code for "Process connection", option FMW |   |           |           |  |  |  |  |  |
|--|---|-----------|-----------|--|--|--|--|--|
| DN<br>[mm]   | A<br>[in]   | B<br>[mm] | L<br>[mm] |  |  |  |  |  |
| 8  | Rd 34 × 1/8   | 16        | 367       |  |  |  |  |  |
| 15   | Rd 34 × 1/8   | 16        | 398       |  |  |  |  |  |
| 25   | Rd 52 × 1/ <sub>6</sub>   | 26        | 434       |  |  |  |  |  |
| 40   | Rd 65 × ¼   | 38        | 560       |  |  |  |  |  |
| 50   | Rd 78 × 1/6   | 50        | 720       |  |  |  |  |  |
| 80   | Rd 110 × ¼  | 81        | 900       |  |  |  |  |  |
| 3-A version available: ord   | 3-A version available: order code for "Additional approval" ontion LP in conjunction with |           |           |  |  |  |  |  |

-A version available: order code for "Additional approval", option LP in conjunction with  $Ra_{max}$  = 0.76  $\mu m$ : order code for "Measuring tube material", option SB, SE

| ler code for "Process con | nection", option <b>FLW</b>         |           |           |
|---------------------------|-------------------------------------|-----------|-----------|
| DN<br>[mm]                | A<br>[in]                           | B<br>[mm] | L<br>[mm] |
| 8                         | Rd 28 × <sup>1</sup> / <sub>8</sub> | 10        | 367       |
| 15                        | Rd 34 × <sup>1</sup> / <sub>8</sub> | 16        | 398       |
| 25                        | Rd 52 × <sup>1</sup> / <sub>8</sub> | 26        | 434       |
| 40                        | Rd 65 × ¼                           | 38        | 560       |
| 50                        | Rd 78 × 1/ <sub>6</sub>             | 50        | 720       |
| 80                        | Rd 110 × ¼                          | 81        | 900       |


3-A version available: order code for "Additional approval", option LP in conjunction with

 $Ra_{max} = 0.76 \ \mu$ m: order code for "Measuring tube material", option SB, SE or  $Ra_{max} = 0.38 \ \mu$ m: order code for "Measuring tube material", option SC, SF  $Ra_{max} = 0.38 \ \mu$ m electropolished: order code for "Measuring tube material", option BC

| 1.4404 (316/316L)<br>Order code for "Process connection", option SCS |                                     |           |           |  |  |  |  |  |
|--|-------------------------------------|-----------|-----------|--|--|--|--|--|
| DN<br>[mm]   | A<br>[in]                           | B<br>[mm] | L<br>[mm] |  |  |  |  |  |
| 8  | Rd 40 × <sup>1</sup> / <sub>6</sub> | 22.6      | 367       |  |  |  |  |  |
| 15   | Rd 40 × 1/6                         | 22.6      | 398       |  |  |  |  |  |
| 25   | Rd 40 × $\frac{1}{6}$               | 22.6      | 434       |  |  |  |  |  |
| 40   | Rd 60 × ¼                           | 35.6      | 560       |  |  |  |  |  |
| 50   | Rd 70 × <sup>1</sup> / <sub>6</sub> | 48.6      | 720       |  |  |  |  |  |
| 80   | Rd 98 × $\frac{1}{6}$               | 72.9      | 900       |  |  |  |  |  |

 $\,$  3-A version available: order code for "Additional approval", option LP in conjunction  $\rm Ra_{max}$  = 0.76  $\mu m$ : order code for "Measuring tube material", option SB, SE

### Thread ISO 2853




Length tolerance for dimension L in mm: +1.5 / -2.0

| Thread ISO 2853, for pipe according to ISO 2037<br>1.4404 (316/316L)<br>Order code for "Process connection", option JSF   |                         |           |           |  |  |  |  |  |
|---|-------------------------|-----------|-----------|--|--|--|--|--|
| DN<br>[mm]  | A <sup>1)</sup><br>[mm] | B<br>[mm] | L<br>[mm] |  |  |  |  |  |
| 8   | 37.13                   | 22.6      | 367       |  |  |  |  |  |
| 15 37.13 22.6 398   |                         |           |           |  |  |  |  |  |
| 25  | 37.13                   | 22.6      | 434       |  |  |  |  |  |
| 40  | 52.68                   | 35.6      | 560       |  |  |  |  |  |
| 50  | 64.16                   | 48.6      | 720       |  |  |  |  |  |
| 80  | 91.19                   | 72.9      | 900       |  |  |  |  |  |
| 3-A version available: order code for "Additional approval", option LP in conjunction with<br>Ra <sub>max</sub> = 0.76 μm: order code for "Measuring tube material", option SB, SE or<br>Ra <sub>max</sub> = 0.38 μm: order code for "Measuring tube material", option SC, SF<br>Ra <sub>max</sub> = 0.38 μm electropolished: order code for "Measuring tube material", option BC |                         |           |           |  |  |  |  |  |

1) Max. thread diameter as per ISO 2853 annex A

VCO




Length tolerance for dimension L in mm: +1.5 / -2.0

| 8-VCO-4 (½")<br>1.4404 (316/316L)<br>Order code for "Process connection", option CVS |           |           |           |  |  |  |  |
|--|-----------|-----------|-----------|--|--|--|--|
| DN<br>[mm]   | A<br>[in] | B<br>[mm] | L<br>[mm] |  |  |  |  |
| 8  | AF 1      | 10.2      | 390       |  |  |  |  |

| <b>12-VCO-4 (¾")</b><br><b>1.4404 (316/316L)</b><br>Order code for "Process connection", option CWS |           |           |           |  |  |  |  |
|---|-----------|-----------|-----------|--|--|--|--|
| DN<br>[mm]  | A<br>[in] | B<br>[mm] | L<br>[mm] |  |  |  |  |
| 15  | AF 1½     | 15.7      | 430       |  |  |  |  |

### Accessories



Purge connections/pressure vessel monitoring/rupture disk

### 🛃 2*3*


- 1 Connection nipple for purge connections/pressure vessel monitoring:
- order code for "Sensor options", option CH "Purge connection" Connection nipple with rupture disk: order code for "Sensor option", option CA "Rupture disk" 2

| DN   | А    | L    |
|------|------|------|
| [mm] | [mm] | [mm] |
| 8    | 62   | 216  |
| 15   | 62   | 220  |
| 25   | 62   | 260  |
| 40   | 67   | 310  |
| 50   | 79   | 452  |
| 80   | 101  | 560  |

### Dimensions in US units

### **Compact version**

Compact version



Dimensions for version without overvoltage protection

Order code for "Housing", options B "GT18 dual compartment, 316L", C "GT20 dual compartment aluminum coated"

| DN<br>[in] | A <sup>1)</sup><br>[in] | B <sup>1)</sup><br>[in] | C<br>[in] | D <sup>2)</sup><br>[in] | E<br>[in] | F <sup>2)</sup><br>[in] | G<br>[in] | H <sup>3)</sup><br>[in] | I <sup>3)</sup><br>[in] | K<br>[in] | L<br>[in] |
|------------|-------------------------|-------------------------|-----------|-------------------------|-----------|-------------------------|-----------|-------------------------|-------------------------|-----------|-----------|
| 3/8        | 6.38                    | 4.02                    | 2.36      | 6.50                    | 2.95      | 3.54                    | 0.21      | 10.55                   | 13.5                    | 2.95      | 4)        |
| 1/2        | 6.38                    | 4.02                    | 2.36      | 6.50                    | 2.95      | 3.54                    | 0.33      | 10.55                   | 13.5                    | 2.95      | 4)        |
| 1          | 6.38                    | 4.02                    | 2.36      | 6.50                    | 2.95      | 3.54                    | 0.47      | 10.55                   | 13.5                    | 2.95      | 4)        |
| 1½         | 6.38                    | 4.02                    | 2.36      | 6.50                    | 2.95      | 3.54                    | 0.69      | 10.75                   | 14.88                   | 4.13      | 4)        |
| 2          | 6.38                    | 4.02                    | 2.36      | 6.50                    | 2.95      | 3.54                    | 1.02      | 11.14                   | 16.69                   | 5.55      | 4)        |
| 3          | 6.38                    | 4.02                    | 2.36      | 6.50                    | 2.95      | 3.54                    | 1.59      | 11.89                   | 19.76                   | 7.87      | 4)        |

For version without local display: values - 0.28 in 1)


2) For versions with overvoltage protection (OVP): values + 0.31 in

, 3) 4) For version without local display: values - 0.11 in

Dependent on the respective process connection

### Flange connections

Fixed flange ASME B16.5



Length tolerance for dimension L in inch: +0.06 / -0.08

## Flange according to ASME B16.5: Class 150

1.4404 (F316/F316L): order code for "Process connection", option AAS Allow C22 · order code for "Process connection" ontion AAC

| Alloy CZZ. 01 | uer coue jor Pro | cess connection, | option AAC |           |           |           |
|---------------|------------------|------------------|------------|-----------|-----------|-----------|
| DN<br>[in]    | A<br>[in]        | B<br>[in]        | C<br>[in]  | D<br>[in] | E<br>[in] | L<br>[in] |
| 3/8 1)        | 3.54             | 2.37             | 4 × Ø0.62  | 0.44      | 0.62      | 14.57     |
| 1/2           | 3.54             | 2.37             | 4 × Ø0.62  | 0.44      | 0.62      | 15.91     |
| 1             | 4.33             | 3.13             | 4 × Ø0.62  | 0.56      | 1.05      | 17.32     |
| 11/2          | 4.92             | 3.87             | 4 × Ø0.63  | 0.63      | 1.61      | 21.65     |
| 2             | 5.91             | 4.75             | 4 × Ø0.75  | 0.75      | 2.07      | 28.15     |
| 3             | 7.48             | 6.00             | 4 × Ø0.75  | 0.94      | 3.07      | 33.07     |
| C             |                  | - 10(+- 0/0      | -          |           |           |           |

Surface roughness (flange): Ra 126 to 248 µin

1) DN  $\frac{3}{8}$ " with DN  $\frac{1}{2}$ " flanges as standard

1/2

|            | Flange according to ASME B16.5: Class 150 with reduction in nominal diameter 1.4404 (F316/F316L) |  |           |           |           |           |           |           |  |  |
|------------|--|--|-----------|-----------|-----------|-----------|-----------|-----------|--|--|
| DN<br>[in] | reduction<br>to DN<br>[in]   | Order code for<br>"Process<br>connection",<br>option | A<br>[in] | B<br>[in] | C<br>[in] | D<br>[in] | E<br>[in] | L<br>[in] |  |  |
| 2          | 1½   | AHS  | 5.91      | 4.75      | 4 × Ø0.75 | 0.75      | 2.07      | 21.65     |  |  |
| 3          | 2  | AJS  | 7.48      | 6         | 4 × Ø0.75 | 0.94      | 3.07      | 28.35     |  |  |
| 4          | 3  | ALS  | 9.06      | 7.5       | 8 × Ø0.75 | 0.94      | 4.03      | 34.41     |  |  |
| Surface re | oughness (flang  | e): Ra 126 to 248 µiı                                | 1         |           |           |           |           | ~         |  |  |

Flange according to ASME B16.5: Class 300 1.4404 (F316/F316L): order code for "Process connection", option ABS Alloy C22: order code for "Process connection", option ABC DN В С D Ε L Α [in] [in] [in] [in] [in] [in] [in] 3/8 1) 3.74 2.63  $4 \times Ø0.62$ 0.56 0.62 14.57 3.74

 $4 \times Ø0.62$ 

0.56

0.62

2.63

15.91

| 1.4404 (F31  | Flange according to ASME B16.5: Class 300<br>1.4404 (F316/F316L): order code for "Process connection", option ABS<br>Alloy C22: order code for "Process connection", option ABC |               |           |           |           |           |  |  |  |
|--------------|---|---------------|-----------|-----------|-----------|-----------|--|--|--|
| DN<br>[in]   | A<br>[in]   | B<br>[in]     | C<br>[in] | D<br>[in] | E<br>[in] | L<br>[in] |  |  |  |
| 1            | 4.92  | 3.50          | 4 × Ø0.75 | 0.69      | 1.05      | 17.32     |  |  |  |
| 11/2         | 6.10  | 4.50          | 4 × Ø0.88 | 0.81      | 1.61      | 21.65     |  |  |  |
| 2            | 6.50  | 5.00          | 8 × Ø0.75 | 0.88      | 2.07      | 28.15     |  |  |  |
| 3            | 8.27  | 6.63          | 8 × Ø0.88 | 1.12      | 3.07      | 33.07     |  |  |  |
| Surface roug | hness (flange):   | Ra 126 to 248 | μin       |           |           |           |  |  |  |

1) DN  $\frac{3}{8}$  with DN  $\frac{1}{2}$  flanges as standard

Flange according to ASME B16.5: Class 300 with reduction in nominal diameter 1.4404 (F316/F316L)


| DN<br>[in] | reduction<br>to DN<br>[in] | Order code for<br>"Process<br>connection",<br>option | A<br>[in] | B<br>[in] | C<br>[in] | D<br>[in] | E<br>[in] | L<br>[in] |  |  |
|------------|----------------------------|--|-----------|-----------|-----------|-----------|-----------|-----------|--|--|
| 2          | 1½                         | AIS  | 6.5       | 5         | 8 × Ø0.75 | 0.88      | 2.07      | 24.21     |  |  |
| 3          | 2                          | AKS  | 8.27      | 6.63      | 8 × Ø0.88 | 1.12      | 3.07      | 28.82     |  |  |
| 4          | 3                          | AMS  | 10.04     | 7.87      | 8 × Ø0.88 | 1.25      | 4.03      | 35.2      |  |  |
|            |                            |  |           |           |           |           |           |           |  |  |

Surface roughness (flange): Ra 126 to 248 µin

| .4404 (F316/F316L): order code for "Process connection", option ACS<br>Alloy C22: order code for "Process connection", option ACC |           |           |           |           |           |           |  |  |
|---|-----------|-----------|-----------|-----------|-----------|-----------|--|--|
| DN<br>[in]  | A<br>[in] | B<br>[in] | C<br>[in] | D<br>[in] | E<br>[in] | L<br>[in] |  |  |
| 3/8 1)  | 3.74      | 2.63      | 4 × Ø0.62 | 0.81      | 0.55      | 15.75     |  |  |
| 1/2   | 3.74      | 2.63      | 4 × Ø0.62 | 0.81      | 0.55      | 16.54     |  |  |
| 1   | 4.92      | 3.50      | 4 × Ø0.75 | 0.94      | 0.96      | 19.29     |  |  |
| 1½  | 6.10      | 4.50      | 4 × Ø0.88 | 1.13      | 1.5       | 23.62     |  |  |
| 2   | 6.50      | 5.00      | 8 × Ø0.75 | 1.25      | 1.94      | 29.21     |  |  |
| 3   | 8.27      | 6.63      | 8 × Ø0.88 | 1.5       | 2.9       | 35.43     |  |  |

1) DN  $\frac{3}{8}$ " with DN  $\frac{1}{2}$ " flanges as standard

### Lap joint flange ASME B16.5





Length tolerance for dimension L in inch: +0.06 / -0.08  $\,$ 

| 1.4301 (F3  | Lap joint flange according to ASME B16.5: Class 150<br>1.4301 (F304), wetted parts Alloy C22<br>Order code for "Process connection", option ADC |              |              |           |           |           |           |   |  |  |
|-------------|---|--------------|--------------|-----------|-----------|-----------|-----------|---|--|--|
| DN<br>[in]  | A<br>[in]   | B<br>[in]    | C<br>[in]    | D<br>[in] | E<br>[in] | F<br>[in] | L<br>[in] | L <sub>diff</sub> <sup>1)</sup><br>[in] |  |  |
| 3/8 2)      | 3.54  | 2.37         | 4 × Ø 0.62   | 0.59      | 1.38      | 0.62      | 14.57     | 0                                       |  |  |
| 1/2         | 3.54  | 2.37         | 4 × Ø 0.62   | 0.59      | 1.38      | 0.62      | 15.91     | 0                                       |  |  |
| 1           | 4.33  | 3.13         | 4 × Ø 0.62   | 0.63      | 2         | 1.05      | 17.32     | 0                                       |  |  |
| 11/2        | 4.92  | 3.87         | 4 × Ø 0.62   | 0.63      | 2.88      | 1.61      | 21.65     | 0                                       |  |  |
| 2           | 5.91  | 4.75         | 4 × Ø 0.75   | 0.75      | 3.62      | 2.07      | 28.15     | 0                                       |  |  |
| 3           | 7.48  | 6.00         | 4 × Ø 0.75   | 0.88      | 5         | 3.07      | 33.07     | 0                                       |  |  |
| Surface rou | ighness (fla  | nge): Ra 126 | 6 to 492 µin |           | •         |           | ·         |   |  |  |

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC) DN  $\frac{3}{8}$ " with DN  $\frac{1}{2}$ " flanges as standard

2)

| 1.4301 (F   | Lap joint flange according to ASME B16.5: Class 300<br>1.4301 (F304), wetted parts Alloy C22<br>Order code for "Process connection", option AEC |              |              |           |           |           |           |                              |  |  |
|-------------|---|--------------|--------------|-----------|-----------|-----------|-----------|------------------------------|--|--|
| DN<br>[in]  | A<br>[in]   | B<br>[in]    | C<br>[in]    | D<br>[in] | E<br>[in] | F<br>[in] | L<br>[in] | L <sub>diff</sub> 1)<br>[in] |  |  |
| 3⁄8 2)      | 3.74  | 2.63         | 4 × Ø 0.62   | 0.65      | 1.38      | 0.62      | 14.8      | +0.23                        |  |  |
| 1/2         | 3.74  | 2.63         | 4 × Ø 0.62   | 0.65      | 1.38      | 0.62      | 15.98     | +0.07                        |  |  |
| 1           | 4.92  | 3.50         | 4 × Ø 0.75   | 0.83      | 2         | 1.05      | 17.72     | +0.40                        |  |  |
| 11/2        | 6.10  | 4.50         | 4 × Ø 0.88   | 0.91      | 2.88      | 1.61      | 22.2      | +0.55                        |  |  |
| 2           | 6.50  | 5.00         | 8 × Ø 0.75   | 1         | 3.62      | 2.07      | 28.23     | +0.08                        |  |  |
| 3           | 8.27  | 6.63         | 8 × Ø 0.88   | 1.22      | 5         | 3.07      | 33.57     | +0.50                        |  |  |
| Surface rou | 1ghness (flai   | nge): Ra 126 | 5 to 492 µin |           | 1         |           |           |                              |  |  |

Difference to installation length of the welding neck flange (order code for "Process connection", option 1) AAC)

2) DN  $^3\!\!/_8$  with DN  $^1\!\!/_2$  flanges as standard


| 1.4301 (F                             | Lap joint flange according to ASME B16.5, Class 600<br>1.4301 (F304), wetted parts Alloy C22<br>Order code for "Process connection", option AFC |             |              |           |           |           |           |   |  |
|---------------------------------------|---|-------------|--------------|-----------|-----------|-----------|-----------|---|--|
| DN<br>[in]                            | A<br>[in]   | B<br>[in]   | C<br>[in]    | D<br>[in] | E<br>[in] | F<br>[in] | L<br>[in] | L <sub>diff</sub> <sup>1)</sup><br>[in] |  |
| 3/8 2)                                | 3.74  | 2.63        | 4 × Ø 0.62   | 0.67      | 1.38      | 0.55      | 15.75     | 0                                       |  |
| 1/2                                   | 3.74  | 2.63        | 4 × Ø 0.62   | 0.67      | 1.38      | 0.55      | 16.54     | 0                                       |  |
| 1                                     | 4.92  | 3.50        | 4 × Ø 0.75   | 0.85      | 2         | 0.96      | 19.29     | 0                                       |  |
| 11⁄2                                  | 6.10  | 4.50        | 4 × Ø 0.88   | 0.98      | 2.88      | 1.5       | 23.62     | 0                                       |  |
| 2                                     | 6.50  | 5.00        | 8 × Ø 0.75   | 1.1       | 3.62      | 1.94      | 29.21     | 0                                       |  |
| 3 8.27 6.63 8ר0.88 1.38 5 2.9 35.43 0 |   |             |              |           |           |           |           |   |  |
| Surface rou                           | 1ghness (fla  | nge): Ra 12 | 6 to 492 µin |           |           | 1         |           |   |  |

Difference to installation length of the welding neck flange (order code for "Process connection", option AAC) DN  $^3\!\!/_8$ " with DN  $^1\!\!/_2$ " flanges as standard 1)

2)

### **Clamp connections**

Tri-Clamp





Length tolerance for dimension L in inch: +0.06 / -0.08  $\,$ 

| Tri-Clamp (½"), DIN 11866 series C         1.4404 (316/316L)         Order code for "Process connection", option FDW |  |                         |                       |      |  |  |  |  |
|--|--|-------------------------|-----------------------|------|--|--|--|--|
| DNClampABL[in][in][in][in][in]   |  |                         |                       |      |  |  |  |  |
| 3/8  | <sup>3</sup> ∕ <sub>8</sub> <sup>1</sup> ∕ <sub>2</sub> 0.98 0.37 14.4 |                         |                       |      |  |  |  |  |
| 1/2  | 1/2  | 0.98                    | 0.37                  | 15.7 |  |  |  |  |
| 3-A version available  | e: order code for "Additior  | al approval", option LF | o in conjunction with |      |  |  |  |  |


3-A version available: order code for "Additional approval", option LP in conjunction  $Ra_{max} = 30 \ \mu$ in: order code for "Measuring tube material", option SB, SE or  $Ra_{max} = 15 \ \mu$ in: order code for "Measuring tube material", option SC, SF  $Ra_{max} = 15 \ \mu$ in electropolished: order code for "Measuring tube material", option BC

| Tri-Clamp ( ≥ 1"), DIN 11866 series C         1.4404 (316/316L)         Order code for "Process connection", option FTS |  |           |           |           |  |  |  |  |
|---|--|-----------|-----------|-----------|--|--|--|--|
| DN<br>[in]  | Clamp<br>[in]  | A<br>[in] | B<br>[in] | L<br>[in] |  |  |  |  |
| 3/8   | 1  | 1.98      | 0.87      | 14.4      |  |  |  |  |
| 1/2   | 1  | 1.98      | 0.87      | 15.7      |  |  |  |  |
| 1   | 1  | 1.98      | 0.87      | 17.1      |  |  |  |  |
| 1½  | 11/2   | 1.98      | 1.37      | 22.0      |  |  |  |  |
| 2   | 2  | 2.52      | 1.87      | 28.3      |  |  |  |  |
| 3   | 3  | 3.58      | 2.87      | 35.4      |  |  |  |  |
| Ra <sub>max</sub> = 30 µin: order   | 3-A version available: order code for "Additional approval", option LP in conjunction with<br>Ra <sub>max</sub> = 30 µin: order code for "Measuring tube material", option SB, SE or<br>Ra <sub>max</sub> = 15 µin: order code for "Measuring tube material" option SC. SF |           |           |           |  |  |  |  |

 $Ra_{max}=15~\mu in:$  order code for "Measuring tube material", option SC, SF  $Ra_{max}=15~\mu in$  electropolished: order code for "Measuring tube material", option BC

### Threaded couplings

Thread SMS 1145




Length tolerance for dimension L in inch: +0.06 / -0.08

| Thread SMS 1145         1.4404 (316/316L)         Order code for "Process connection", option SCS |                                     |           |           |  |  |  |  |  |
|---|-------------------------------------|-----------|-----------|--|--|--|--|--|
| DN<br>[in]  | A<br>[in]                           | B<br>[in] | L<br>[in] |  |  |  |  |  |
| 3⁄8   | Rd 40 × 1/ <sub>6</sub>             | 0.89      | 14.45     |  |  |  |  |  |
| 1/2   | Rd 40 × <sup>1</sup> / <sub>6</sub> | 0.89      | 15.67     |  |  |  |  |  |
| 1   | Rd 40 × 1/ <sub>6</sub>             | 0.89      | 17.09     |  |  |  |  |  |
| 11/2  | Rd 60 × ¼                           | 1.4       | 22.05     |  |  |  |  |  |
| 2   | Rd 70 × <sup>1</sup> / <sub>6</sub> | 1.91      | 28.35     |  |  |  |  |  |
| 3   | Rd 98 × ¼                           | 2.87      | 35.43     |  |  |  |  |  |

3-A version available: order code for "Additional approval", option LP in conjunction with  $Ra_{max} = 30 \ \mu$ in: order code for "Measuring tube material", option SB, SE

VCO






Length tolerance for dimension L in inch: +0.06 / -0.08

| 8-VCO-4 (½")<br>1.4404 (316/316L)<br>Order code for "Process cor |           |           |           |  |  |  |  |  |
|--|-----------|-----------|-----------|--|--|--|--|--|
| DN<br>[in]   | A<br>[in] | B<br>[in] | L<br>[in] |  |  |  |  |  |
| 3/8  | AF 1      | 0.4       | 15.35     |  |  |  |  |  |

| <b>12-VCO-4 (¾")</b><br><b>1.4404 (316/316L)</b><br>Order code for "Process co | onnection", option <b>CWS</b> |           |           |
|--|-------------------------------|-----------|-----------|
| DN<br>[in]   | A<br>[in]                     | B<br>[in] | L<br>[in] |
| 1/2  | AF 1½                         | 0.62      | 16.93     |

### Accessories

Purge connections / secondary containment monitoring Order code for "Sensor options", option CH



| DN   | G     | Н    | L     |
|------|-------|------|-------|
| [in] | [in]  | [in] | [in]  |
| 3/8  | ½ NPT | 2.44 | 8.50  |
| 1/2  | ½ NPT | 2.44 | 8.66  |
| 1    | ½ NPT | 2.44 | 10.24 |
| 1½   | ½ NPT | 2.64 | 12.20 |
| 2    | ½ NPT | 3.11 | 17.78 |
| 3    | ½ NPT | 3.98 | 22.0  |

### Weight

All values (weight) refer to devices with EN/DIN PN 40 flanges.

### Weight in SI units

| DN   | Weight [kg]   |   |  |
|------|---|---|--|
| [mm] | Order code for "Housing", option C<br>Aluminum coated | Order code for "Housing", option B<br>1.4404 (316L) |  |
| 8    | 9   | 11.5  |  |
| 15   | 10  | 12.5  |  |
| 25   | 12  | 14.5  |  |
| 40   | 17  | 19.5  |  |
| 50   | 28  | 30.5  |  |
| 80   | 53  | 55.5  |  |

### Weight in US units


| DN   | Weight [lbs]  |   |  |
|------|---|---|--|
| [in] | Order code for "Housing", option C<br>Aluminum coated | Order code for "Housing", option B<br>1.4404 (316L) |  |
| 3/8  | 20  | 25  |  |
| 1/2  | 22  | 28  |  |
| 1    | 26  | 32  |  |
| 11/2 | 37  | 43  |  |
| 2    | 62  | 67  |  |
| 3    | 117   | 122   |  |

### Materials

### Transmitter housing

- Order code for "Housing", option **B**: stainless steel CF-3M (316L, 1.4404)
- Order code for "Housing", option C "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
- Window material: glass

### Cable entries/cable glands



24 Possible cable entries/cable glands

- 1 Cable entry with M20 × 1.5 internal thread
- 2 Cable gland  $M20 \times 1.5$
- 3 Adapter for cable entry with internal thread G  $\frac{1}{2}$  or NPT  $\frac{1}{2}$

Order code for "Housing", option B "GT18 two-chamber, 316L"

| Cable entry/cable gland                             | Type of protection   | Material                       |
|---|--|--------------------------------|
| Cable gland M20 × 1.5                               | <ul> <li>Non-Ex</li> <li>Ex ia</li> <li>Ex ic</li> <li>Ex nA</li> <li>Ex tb</li> </ul> | Stainless steel ,1.4404        |
| Adapter for cable entry with internal thread G ½"   | For non-Ex and Ex<br>(except for CSA Ex d/XP)  | Stainless steel, 1.4404 (316L) |
| Adapter for cable entry with internal thread NPT ½" | For non-Ex and Ex  |                                |

| Cable entry/cable gland                             | Type of protection                                   | Material            |
|---|--|---------------------|
| Cable gland M20 × 1.5                               | <ul><li>Non-Ex</li><li>Ex ia</li><li>Ex ic</li></ul> | Plastic             |
|   | Adapter for cable entry with internal thread G ½"    | Nickel-plated brass |
| Adapter for cable entry with internal thread NPT ½" | For non-Ex and Ex<br>(except for CSA Ex d/XP)        | Nickel-plated brass |
| Thread NPT ½"<br>via adapter                        | For non-Ex and Ex                                    |                     |

Order code for "Housing", option C "GT20 dual compartment, aluminum coated"

### **Device** plug

| Electrical connection | Material   |
|-----------------------|--|
| Plug M12x1            | <ul> <li>Socket: stainless steel, 1.4401/316</li> <li>Contact housing: plastic, PUR, black</li> <li>Contacts: metal, CuZn, gold-plated</li> <li>Threaded connection seal: NBR</li> </ul> |

### Sensor housing

- Acid and alkali-resistant outer surface
- stainless steel, 1.4301 (304)
   Optional: order code for "Sensor option", option CC: stainless steel, 1.4404 (316L)

### Measuring tubes

- DN 8 to 80 (3/8 to 3"): stainless steel, 1.4539 (904L);
- Manifold: stainless steel, 1.4404 (316/316L)
- DN 8 to 80 (3/8 to 3"): Alloy C22, 2.4602 (UNS N06022); Manifold: Alloy C22, 2.4602 (UNS N06022)

### **Process connections**

- Flanges according to EN 1092-1 (DIN2501) / according to ASME B 16.5 / as per JIS B2220:
  - Stainless steel, 1.4404 (F316/F316L)
  - Alloy C22, 2.4602 (UNS N06022)
  - Lap joint flanges: stainless steel, 1.4301 (F304); wetted parts Alloy C22
- All other process connections: Stainless steel, 1.4404 (316/316L)

List of all available process connections  $\rightarrow \square 70$ 

### Seals

Welded process connections without internal seals

### Accessories

Protective cover

Stainless steel, 1.4404 (316L)

| Process connections | <ul> <li>Fixed flange connections:</li> </ul>  |  |  |
|---------------------|--|--|--|
|                     | <ul> <li>EN 1092-1 (DIN 2501) flange</li> <li>EN 1092-1 (DIN 2512N) flange</li> <li>Namur lengths in accordance with NE 132</li> </ul> |  |  |
|                     |  |  |  |
|                     |  |  |  |
|                     | <ul> <li>ASME B16.5 flange</li> </ul>  |  |  |
|                     | ■ JIS B2220 flange   |  |  |
|                     | <ul> <li>DIN 11864-2 Form A flange, DIN11866 series A, flange with notch</li> </ul>  |  |  |
|                     | <ul> <li>Clamp connections</li> </ul>  |  |  |
|                     | Tri-Clamp (OD tubes), DIN 11866 series C   |  |  |
|                     | Threads:   |  |  |
|                     | <ul> <li>DIN 11851 thread, DIN11866 series A</li> </ul>  |  |  |
|                     | <ul> <li>SMS 1145 thread</li> </ul>  |  |  |
|                     | <ul> <li>ISO 2853 thread, ISO2037</li> </ul>   |  |  |
|                     | <ul> <li>DIN 11864-1 Form A thread, DIN11866 series A</li> </ul>   |  |  |
|                     | <ul> <li>VCO connections</li> </ul>  |  |  |
|                     | ■ 8-VCO-4  |  |  |
|                     | ■ 12-VCO-4   |  |  |
|                     | For information on the different materials used in the process connections $\rightarrow \cong 68$                                      |  |  |
| Surface roughness   | All data relate to parts in contact with fluid. The following surface roughness quality can be ordered<br>• Not polished               |  |  |
|                     | • $Ra_{max} = 0.76 \ \mu m \ (30 \ \mu in)$  |  |  |
|                     | • $Ra_{max} = 0.38 \ \mu m (15 \ \mu m)$   |  |  |

Ra<sub>max</sub> = 0.38 μm (15 μin)
 Ra<sub>max</sub> = 0.38 μm (15 μin) electropolished


# Operability

| Operating concept | Operator-oriented menu structure for user-specific tasks <ul> <li>Commissioning</li> <li>Operation</li> <li>Diagnostics</li> <li>Expert level</li> </ul> <li>Quick and safe commissioning</li>  |  |  |
|-------------------|---|--|--|
|                   | <ul> <li>Guided menus ("Make-it-run" wizards) for applications</li> <li>Menu guidance with brief explanations of the individual parameter functions</li> </ul>  |  |  |
|                   | <ul> <li>Reliable operation</li> <li>Operation in the following languages: <ul> <li>Via local display:</li> <li>English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Swedish, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech</li> <li>Via "FieldCare" operating tool:</li> <li>English, German, French, Spanish, Italian, Chinese, Japanese</li> </ul> </li> <li>Uniform operating philosophy applied to device and operating tools</li> <li>If replacing the electronic module, transfer the device configuration via the integrated memory (integrated HistoROM) which contains the process and measuring device data and the event logbook. No need to reconfigure.</li> </ul> |  |  |
|                   | <ul> <li>Efficient diagnostics increase measurement availability</li> <li>Troubleshooting measures can be called up via the device and in the operating tools</li> <li>Diverse simulation options, logbook for events that occur and optional line recorder functions</li> </ul>  |  |  |
| Languages         | <ul> <li>Can be operated in the following languages:</li> <li>Via local display:<br/>English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Swedish, Turkish,<br/>Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech</li> <li>Via "FieldCare" operating tool:<br/>English, German, French, Spanish, Italian, Chinese, Japanese</li> </ul>  |  |  |

### Local operation

### Via display module

Two display modules are available:



### Display elements

- 4-line, illuminated, graphic display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
   Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F)
  - The readability of the display may be impaired at temperatures outside the temperature range.


### **Operating elements**

- Operation with 3 push buttons with open housing: 🗉, 🖃, 🗉
- or
- - Operating elements also accessible in various hazardous areas

### Additional functionality

- Data backup function
- The device configuration can be saved in the display module.
- Data comparison function The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function The transmitter configuration can be transmitted to another device using the display module.

### Via remote display and operating module FHX50




### ☑ 25 FHX50 operating options

- 1 SD02 display and operating module, push buttons: cover must be opened for operation
- 2 SD03 display and operating module, optical buttons: operation possible through cover glass

### **Remote operation**

### Via HART protocol

This communication interface is available in device versions with a HART output.




26 Options for remote operation via HART protocol (passive)

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 VIATOR Bluetooth modem with connecting cable
- 9 Transmitter

## Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.




■ 27 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Segment coupler PROFIBUS DP/PA
- 5 PROFIBUS PA network
- 6 T-box
- 7 Measuring device

### Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




28 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- 3 Industry network
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device

### Service interface

# Via service interface (CDI)



1 Service interface (CDI = Endress+Hauser Common Data Interface) of the measuring device

- 2 Commubox FXA291
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

# **Certificates and approvals**

| CE mark           | The measuring system is in conformity with the statutory requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.   |
|-------------------|---|
|                   | Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.   |
| C-Tick symbol     | The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".  |
| Functional safety | The measuring device can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture; order code for "Additional approval", option <b>LA</b> ) and SIL 3 (multichannel architecture with homogeneous redundancy) and is independently evaluated and certified by the TÜV in accordance with IEC 61508. |
|                   | The following types of monitoring in safety equipment are possible:<br>Mass flow<br>Volume flow<br>Density  |
|                   | Functional Safety Manual with information on the SIL device $\rightarrow \cong 81$  |
| Ex approval       | The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document or the nameplate.  |
|                   | The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.  |
|                   | ATEX/IECEx  |

Currently, the following versions for use in hazardous areas are available:

#### Ex d

| Category (ATEX) | Type of protection  |
|-----------------|---|
| II2G            | Ex d[ia] IIC T6T1 Gb<br>or Ex d[ia] IIB T6T1 Gb <sup>1)</sup>                               |
| II1/2G          | Ex d[ia] IIC T6T1 Ga/Gb<br>or Ex d[ia] IIB T6T1 Ga/Gb <sup>1)</sup>                         |
| II1/2G, II2D    | Ex d[ia] IIC T6T1 Ga/Gb<br>or Ex d[ia] IIB T6T1 Ga/Gb <sup>1)</sup><br>Ex tb IIIC Txx °C Db |

#### 1) For sensors with nominal diameter DN 80

### Ex ia

| Category (ATEX) | Type of protection  |
|-----------------|---|
| II2G            | Ex ia IIC T6T1 Gb<br>or Ex ia IIB T6T1 Gb <sup>1)</sup>                               |
| II1/2G          | Ex ia IIC T6T1 Ga/Gb<br>or Ex ia IIB T6T1 Ga/Gb <sup>1)</sup>                         |
| II1/2G, II2D    | Ex ia IIC T6T1 Ga/Gb<br>or Ex ia IIB T6T1 Ga/Gb <sup>1)</sup><br>Ex tb IIIC Txx °C Db |

1) For sensors with nominal diameter DN 80

### Ex nA

| Category (ATEX) | Type of protection |
|-----------------|--------------------|
| II3G            | Ex nA IIC T6T1 Gc  |

### Ex ic

| Category (ATEX) | Type of protection  |
|-----------------|---|
| II3G            | Ex ic IIC T6T1 Gc<br>or Ex ic IIB T6T1 Gc <sup>1)</sup>               |
| II1/3G          | Ex ic[ia] IIC T6T1 Ga/Gc<br>or Ex ic[ia] IIB T6T1 Ga/Gc <sup>1)</sup> |

1) For sensors with nominal diameter DN 80

# $_{\rm C}{\rm CSA}_{\rm US}$

Currently, the following versions for use in hazardous areas are available:

|                        | IS (Ex i) and XP (Ex d)<br>Class I, II, III Division 1 Groups ABCDEFG<br>For sensors with nominal diameter DN 80: Class I, II, III Division 1 Groups CDEFG  |
|------------------------|---|
|                        | <ul> <li>NI (Ex nA, Ex nL)</li> <li>Class I Division 2 Groups ABCD</li> <li>Class II, III Division 1 Groups EFG</li> </ul>  |
| Sanitary compatibility | <ul><li> 3-A approval</li><li> EHEDG-tested</li></ul>   |
| Functional safety      | The measuring device can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture; order code for "Additional approval", option <b>LA</b> ) and SIL 3 (multichannel architecture with homogeneous redundancy) and is independently evaluated and certified by the TÜV in accordance with IEC 61508. |

The following types of monitoring in safety equipment are possible: Mass flow Volume flow Density Functional Safety Manual with information on the SIL device  $\rightarrow \square 81$ HART certification HART interface The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications: Certified according to HART 7 • The device can also be operated with certified devices of other manufacturers (interoperability) **FOUNDATION Fieldbus** FOUNDATION Fieldbus interface certification The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications: • Certified in accordance with FOUNDATION Fieldbus H1 • Interoperability Test Kit (ITK), revision version 6.1.1 (certificate available on request) Physical Layer Conformance Test The device can also be operated with certified devices of other manufacturers (interoperability) **Certification PROFIBUS PROFIBUS** interface The measuring device is certified and registered by the PROFIBUS User Organization (PNO). The measuring system meets all the requirements of the following specifications: • Certified in accordance with PROFIBUS PA Profile 3.02 • The device can also be operated with certified devices of other manufacturers (interoperability) **Pressure Equipment** The devices can be ordered with or without a PED approval. If a device with a PED approval is Directive required, this must be explicitly stated in the order. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary. • With the identification PED/G1/x (x = category) on the sensor nameplate, Endress+Hauser confirms conformity with the "Essential Safety Requirements" specified in Appendix I of the Pressure Equipment Directive 2014/68/EC. • Devices bearing this marking (PED) are suitable for the following types of medium: • Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to0.5 bar (7.3 psi) Unstable gases • Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Art. 4, Par. 3 of the Pressure Equipment Directive 2014/68/EU. The range of application is indicated in tables 6 to 9 in Annex II of the Pressure Equipment Directive 2014/68/EC. Other standards and EN 60529 Degrees of protection provided by enclosures (IP code) auidelines IEC/EN 60068-2-6 Environmental influences: Test procedure - Test Fc: vibrate (sinusoidal). ■ IEC/EN 60068-2-31 Environmental influences: Test procedure - Test Ec: shocks due to rough handling, primarily for devices. EN 61010-1 Safety requirements for electrical equipment for measurement, control and laboratory use general requirements IEC/EN 61326 Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements). IEC 61508 Functional safety of electrical/electronic/programmable electronic safety-related systems NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment NAMUR NE 32 Data retention in the event of a power failure in field and control instruments with microprocessors

NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

- NAMUR NE 53
- Software of field devices and signal-processing devices with digital electronics • NAMUR NE 80
- The application of the pressure equipment directive to process control devices • NAMUR NE 105
- Specifications for integrating fieldbus devices in engineering tools for field devices
- NAMUR NE 107 Self-monitoring and diagnosis of field devices
- NAMUR NE 131
- Requirements for field devices for standard applications
- NAMUR NE 132
- Coriolis mass meter
- NACE MR0103
- Materials resistant to sulfide stress cracking in corrosive petroleum refining environments.
- NACE MR0175/ISO 15156-1 Materials for use in H2S-containing Environments in Oil and Gas Production.

# Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
   -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
   Open product page -> The "Configure" button to the right of the product image opens the Product
   Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

# Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
  - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
  - Automatic verification of exclusion criteria
  - Automatic creation of the order code and its breakdown in PDF or Excel output format
  - Ability to order directly in the Endress+Hauser Online Shop

# **Application packages**

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

| Diagnostics functions | Package           | Description  |
|-----------------------|-------------------|--|
|                       | Extended HistoROM | Comprises extended functions concerning the event log and the activation of the measured value memory.   |
|                       |                   | Event log:<br>Memory volume is extended from 20 message entries (standard version) to up to<br>100 entries.  |
|                       |                   | <ul> <li>Data logging (line recorder):</li> <li>Memory capacity for up to 1000 measured values is activated.</li> <li>250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user.</li> <li>Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server.</li> </ul> |

# Heartbeat Technology

| Package                | Description  |  |
|------------------------|--|--|
| Heartbeat Verification | <ul> <li>Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment".</li> <li>Functional testing in the installed state without interrupting the process.</li> <li>Traceable verification results on request, including a report.</li> <li>Simple testing process via local operation or other operating interfaces.</li> <li>Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.</li> <li>Extension of calibration intervals according to operator's risk assessment.</li> </ul> |  |

# Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

### Device-specific accessories

For the transmitter

| Accessories             | Description  |
|-------------------------|--|
| Promass 200 transmitter | Transmitter for replacement or storage. Use the order code to define the following<br>specifications:<br>• Approvals<br>• Output<br>• Display / operation<br>• Housing<br>• Software<br>For details, see Installation Instructions EA00104D  |
| Remote display<br>FHX50 | <ul> <li>FHX50 housing for accommodating a display module .</li> <li>FHX50 housing suitable for: <ul> <li>SD02 display module (push buttons)</li> <li>SD03 display module (touch control)</li> </ul> </li> <li>Housing material: <ul> <li>Plastic PBT</li> <li>Stainless steel CF-3M (316L, 1.4404)</li> </ul> </li> <li>Length of connecting cable: up to max. 60 m (196 ft) (cable lengths available for order: 5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft))</li> </ul>  |
|                         | <ul> <li>The measuring device can be ordered with the FHX50 housing and a display module. The following options must be selected in the separate order codes:</li> <li>Order code for measuring device, feature 030:<br/>Option L or M "Prepared for FHX50 display"</li> <li>Order code for FHX50 housing, feature 050 (device version):<br/>Option A "Prepared for FHX50 display"</li> <li>Order code for FHX50 housing, depends on the desired display module in feature 020 (display, operation):</li> <li>Option C: for an SD02 display module (push buttons)</li> <li>Option E: for an SD03 display module (touch control)</li> </ul> |
|                         | <ul> <li>The FHX50 housing can also be ordered as a retrofit kit. The measuring device display module is used in the FHX50 housing. The following options must be selected in the order code for the FHX50 housing:</li> <li>Feature 050 (measuring device version): option B "Not prepared for FHX50 display"</li> <li>Feature 020 (display, operation): option A "None, existing displayed used"</li> <li>For details, see Special Documentation SD01007F</li> </ul>   |
|                         | (Order number: FHX50)  |

| Overvoltage protection for 2-wire devices | <ul> <li>Ideally, the overvoltage protection module should be ordered directly with the device. See product structure, characteristic 610 "Accessory mounted", option NA "Overvoltage protection". Separate order necessary only if retrofitting.</li> </ul> |  |
|---|--|--|
|   | <ul> <li>OVP10: For 1-channel devices (characteristic 020, option A):</li> <li>OVP20: For 2-channel devices (characteristic 020, options B, C, E or G)</li> <li>For details, see Special Documentation SD01090F.</li> </ul>                                  |  |
| Protective cover                          | Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight or extreme cold in winter.<br>For details, see Special Documentation SD00333F   |  |

## For the sensor

| Accessories    | Description  |
|----------------|--|
| Heating jacket | Is used to stabilize the temperature of the fluids in the sensor.<br>Water, water vapor and other non-corrosive liquids are permitted for use as fluids.<br>If using oil as a heating medium, please consult with Endress+Hauser.<br>Heating jackets cannot be used with sensors fitted with a rupture disk. |
|                | For details, see Operating Instructions BA00132D   |

| Communication-specific<br>accessories | Accessories                    | Description  |
|---------------------------------------|--------------------------------|--|
| accessories                           | Commubox FXA195                | For intrinsically safe HART communication with FieldCare via the USB interface.  |
|                                       | HART                           | For details, see "Technical Information" TI00404F  |
|                                       | Commubox FXA291                | Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser<br>Common Data Interface) and the USB port of a computer or laptop.   |
|                                       |                                | For details, see the "Technical Information" document TI405C/07  |
|                                       | HART Loop Converter<br>HMX50   | Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.  |
|                                       |                                | For details, see "Technical Information" TI00429F and Operating Instructions BA00371F  |
|                                       | Wireless HART adapter<br>SWA70 | Is used for the wireless connection of field devices.<br>The WirelessHART adapter can be easily integrated into field devices and existing<br>infrastructures, offers data protection and transmission safety and can be operated<br>in parallel with other wireless networks with minimum cabling complexity. |
|                                       |                                | For details, see Operating Instructions BA00061S   |
|                                       | Fieldgate FXA320               | Gateway for the remote monitoring of connected 4 to 20 mA measuring devices via a Web browser.   |
|                                       |                                | For details, see "Technical Information" TI00025S and Operating Instructions BA00053S  |
|                                       | Fieldgate FXA520               | Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser.   |
|                                       |                                | For details, see "Technical Information" TI00025S and Operating Instructions BA00051S  |
|                                       | Field Xpert SFX350             | Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the <b>non-Ex area</b> .  |
|                                       |                                | For details, see Operating Instructions BA01202S   |
|                                       | Field Xpert SFX370             | Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the <b>non-Ex area</b> and the <b>Ex area</b> .   |
|                                       |                                | For details, see Operating Instructions BA01202S   |

| Service-specific accessories | Accessories | Description   |
|------------------------------|-------------|---|
|                              | Applicator  | <ul> <li>Software for selecting and sizing Endress+Hauser measuring devices:</li> <li>Choice of measuring devices for industrial requirements</li> <li>Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy.</li> <li>Graphic illustration of the calculation results</li> <li>Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.</li> </ul>  |
|                              |             | <ul> <li>Applicator is available:</li> <li>Via the Internet: https://wapps.endress.com/applicator</li> <li>As a downloadable DVD for local PC installation.</li> </ul>  |
|                              | W@M         | W@M Life Cycle Management<br>Improved productivity with information at your fingertips. Data relevant to a plant<br>and its components is generated from the first stages of planning and during the<br>asset's complete life cycle.<br>W@M Life Cycle Management is an open and flexible information platform with<br>online and on-site tools. Instant access for your staff to current, in-depth data<br>shortens your plant's engineering time, speeds up procurement processes and<br>increases plant uptime.<br>Combined with the right services, W@M Life Cycle Management boosts<br>productivity in every phase. For more information, visit<br>www.endress.com/lifecyclemanagement |
|                              | FieldCare   | FDT-based plant asset management tool from Endress+Hauser.<br>It can configure all smart field units in your system and helps you manage them. By<br>using the status information, it is also a simple but effective way of checking their<br>status and condition.<br>For details, see Operating Instructions BA00027S and BA00059S  |
|                              | DeviceCare  | Tool for connecting and configuring Endress+Hauser field devices.   |

## System components

| Accessories                             | Description   |  |
|---|---|--|
| Memograph M graphic<br>display recorder | The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick. |  |
|   | For details, see "Technical Information" TI00133R and Operating Instructions BA00247R   |  |
| RN221N                                  | Active barrier with power supply for safe separation of 4-20 mA standard signal circuits. Offers bidirectional HART transmission.   |  |
|   | For details, see "Technical Information" TI00073R and Operating Instructions BA00202R   |  |
| RNS221                                  | Supply unit for powering two 2-wire measuring devices solely in the non-Ex area.<br>Bidirectional communication is possible via the HART communication jacks.   |  |
|   | For details, see "Technical Information" TI00081R and Brief Operating<br>Instructions KA00110R  |  |
| Cerabar M                               | The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.   |  |
|   | For details, see "Technical Information" TI00426P, TI00436P and Operating Instructions BA00200P, BA00382P   |  |
| Cerabar S                               | The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.   |  |
|   | For details, see "Technical Information" TI00383P and Operating Instructions BA00271P   |  |

# Documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

- The *W@M Device Viewer* : Enter the serial number from the nameplate (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

# Standard documentation Brief Operating Instructions

#### Part 1 of 2: Sensor

| Measuring device  | Documentation code |
|-------------------|--------------------|
| Proline Promass F | KA01260D           |

### Part 2 of 2: Transmitter

|                        | Documentation code |                     |             |
|------------------------|--------------------|---------------------|-------------|
| Measuring device       | HART               | FOUNDATION Fieldbus | PROFIBUS PA |
| Proline Promass<br>200 | KA012268           | KA01267D            | KA01269D    |

### **Operating Instructions**

|                          | Documentation code |                     |             |
|--------------------------|--------------------|---------------------|-------------|
| Measuring device         | HART               | FOUNDATION Fieldbus | PROFIBUS PA |
| Proline Promass F<br>200 | BA01112D           | BA01315D            | BA01113D    |

### Description of device parameters

|                        | Documentation code |                     |             |
|------------------------|--------------------|---------------------|-------------|
| Measuring device       | HART               | FOUNDATION Fieldbus | PROFIBUS PA |
| Proline Promass<br>200 | GP01010D           | GP01030D            | GP01029D    |

### Supplementary devicedependent documentation

#### Safety instructions

| Content          | Documentation code |
|------------------|--------------------|
| ATEX/IECEx Ex i  | XA00144D           |
| ATEX/IECEx Ex d  | XA00143D           |
| ATEX/IECEx Ex nA | XA00145D           |
| cCSAus IS        | XA00151D           |
| cCSAus XP        | XA00152D           |
| INMETRO Ex i     | XA01300D           |
| INMETRO Ex d     | XA01305D           |
| INMETRO Ex nA    | XA01306D           |
| NEPSI Ex i       | XA00156D           |
| NEPSI Ex d       | XA00155D           |
| NEPSI Ex nA      | XA00157D           |

### **Special Documentation**

| Content   | Documentation code |
|---|--------------------|
| Information on the Pressure Equipment Directive | SD01614D           |
| Functional Safety Manual                        | SD00147D           |
| Display and operating module FHX50              | SD01007F           |

| Content              | Documentation |                     |             |
|----------------------|---------------|---------------------|-------------|
|                      | HART          | FOUNDATION Fieldbus | PROFIBUS PA |
| Heartbeat Technology | SD01849D      | SD01848D            | SD01850D    |

## Installation Instructions

| Contents                                      | Documentation code                      |
|---|---|
| Installation Instructions for spare part sets | Specified for each individual accessory |

# **Registered trademarks**

# HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

### **PROFIBUS**<sup>®</sup>

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

### FOUNDATION<sup>TM</sup> Fieldbus

Registration-pending trademark of the FieldComm Group, Austin, Texas, USA

## TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA

**Applicator®**, **FieldCare®**, **DeviceCare ®**, **Field Xpert<sup>TM</sup>**, **HistoROM®**, **Heartbeat Technology<sup>TM</sup>** Registered or registration-pending trademarks of the Endress+Hauser Group



www.addresses.endress.com

