

Safety Instructions

Proline Promass 300

Class I, Zone 1
Zone 21



Proline Promass 300

Table of contents

| | |
|---|----|
| About this document | 4 |
| Associated documentation | 4 |
| Certificates and declarations | 5 |
| Manufacturer address | 5 |
| Extended order code | 5 |
| Safety instructions: General | 9 |
| Safety instructions: Installation | 10 |
| Safety instructions: Zone 21 | 13 |
| Temperature tables | 13 |
| Explosion hazards arising from gas and dust | 24 |
| Connection values: Signal circuits | 26 |

About this document



The document number of these Safety Instructions (XA) must match the information on the nameplate.

Associated documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:

- *Device Viewer* (www.endress.com/deviceviewer): Enter serial number from nameplate.
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

To commission the device, please observe the Operating Instructions pertaining to the device:

| Measuring device | Documentation code | | | |
|----------------------|--------------------|---------------------|-------------|-------------|
| | HART | FOUNDATION Fieldbus | PROFIBUS PA | PROFIBUS DP |
| Promass A 300 (8A3B) | BA01482D | BA01515D | BA01504D | – |
| Promass A 300 (8A3C) | BA01816D | BA01843D | BA01841D | BA01857D |
| Promass E 300 | BA01484D | BA01517D | BA01506D | BA01855D |
| Promass F 300 | BA01485D | BA01518D | BA01507D | BA01850D |
| Promass H 300 | BA01486D | BA01519D | BA01508D | BA01858D |
| Promass I 300 | BA01487D | BA01520D | BA01509D | BA01859D |
| Promass O 300 | BA01488D | BA01521D | BA01510D | BA01860D |
| Promass P 300 | BA01489D | BA01522D | BA01511D | BA01861D |
| Promass Q 300 | BA01490D | BA01523D | BA01512D | BA01862D |
| Promass S 300 | BA01491D | BA01524D | BA01513D | BA01863D |
| Promass X 300 | BA01492D | BA01525D | BA01514D | BA01864D |

| Measuring device | Documentation code | | |
|----------------------|--------------------|-------------|----------|
| | Modbus RS485 | EtherNet/IP | PROFINET |
| Promass A 300 (8A3B) | BA01493D | BA01699D | BA01736D |
| Promass A 300 (8A3C) | BA01884D | BA01842D | BA01840D |
| Promass E 300 | BA01495D | BA01727D | BA01738D |
| Promass F 300 | BA01496D | BA01728D | BA01739D |
| Promass H 300 | BA01497D | BA01729D | BA01740D |
| Promass I 300 | BA01498D | BA01730D | BA01741D |
| Promass O 300 | BA01499D | BA01731D | BA01742D |
| Promass P 300 | BA01500D | BA01732D | BA01743D |

| Measuring device | Documentation code | | |
|------------------|--------------------|-------------|----------|
| | Modbus RS485 | EtherNet/IP | PROFINET |
| Promass Q 300 | BA01501D | BA01733D | BA01744D |
| Promass S 300 | BA01502D | BA01734D | BA01745D |
| Promass X 300 | BA01503D | BA01735D | BA01746D |

Additional documentation

| Contents | Document type | Documentation code |
|--|---|-----------------------------|
| Remote display and operating module DKX001 | Special documentation | SD01763D |
| | Safety Instructions Zone 1, Zone 2 1; Class I, Division 1 | XA01499D |
| Explosion Protection | Brochure | CP0002 1Z/11 |
| Ethernet-APL Installation Drawing | Installation Drawing | HE_01622 |
| Control drawing | | As wanted on the nameplate. |

Please note the documentation associated with the device.

Certificates and declarations

Certificate number

CSA 16.70087366

Notified body

CSA Group


Manufacturer address

Endress+Hauser Flowtec AG
Kägenstrasse 7
4153 Reinach BL
Switzerland

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code



* = Placeholder
 At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Device type

The device and the device design is defined in the "Device type" section (Product root).

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Device type

| Position | Order code for | Option selected | Description |
|----------|-------------------|--|--|
| 1 | Instrument family | 8 | Coriolis flowmeter |
| 2 | Sensor | A, E, F, H, I, O, P, Q, S, X ¹⁾ | Sensor type |
| 3 | Transmitter | 3 | Transmitter type: 4-wire, compact version |
| 4 | Generation index | B, C | Platform generation |
| 5, 6 | Nominal diameter | Examples: 02, 04, 40, 50, 1H, 3E ^{2) 3)} | Nominal diameter of sensor |

- 1) For replacement transmitter only: X
- 2) For the exact specification of the nominal diameter, see nameplate
- 3) For replacement transmitter only: XX

Basic specifications

| Position 1, 2 Order code for "Approval" Option selected | Position 4, 5 Order code for "Output, input 1" Option selected | Type of protection | |
|---|---|--|---|
| | | Transmitter | Sensor |
| C1 | BA, BB, GA, LA, MA, MB, NA, RA, RB, SA | Cl.I, Zone 1, AEx/Ex db eb ia IIB T6...T1 Gb Zone 21, AEx/Ex tb IIIC T** °C Db | Cl.I, Zone 1, AEx/Ex ia IIB T6...T1 Gb Zone 21, AEx/ Ex ia tb IIIC T** °C Db |
| | CA, CC, HA, MC, RC, TA | Cl.I, Zone 1, AEx/Ex db eb ia [ia Ga] IIB T6...T1 Gb Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db | |
| C2 | BA, BB, GA, LA, NA, MA, MB, RA, RB, SA, | Cl.I, Zone 1, AEx/Ex db eb ia IIC T6...T1 Gb Zone 21, AEx/Ex tb IIIC T** °C Db | Cl.I, Zone 1, AEx/Ex ia IIC T6...T1 Gb Zone 21, AEx/ Ex ia tb IIIC T** °C Db |
| | CA, CC, HA, MC, RC, TA | Cl.I, Zone 1, AEx/Ex db eb ia [ia Ga] IIC T6...T1 Gb Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db | |
| C3 | BA, BB, GA, LA, MA, MB, NA, RA, RB, SA | Cl.I, Zone 1, AEx/Ex db ia IIB T6...T1 Gb Zone 21, AEx/Ex tb IIIC T** °C Db | Cl.I, Zone 1, AEx/Ex ia IIB T6...T1 Gb Zone 21, AEx/ Ex ia tb IIIC T** °C Db |
| | CA, CC, HA, MC, RC, TA | Cl.I, Zone 1, AEx/Ex db ia [ia Ga] IIB T6...T1 Gb Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db | |
| C4 | BA, BB, GA, LA, MB, NA, RA, RB, SA, MA | Cl.I, Zone 1, AEx/Ex db ia IIC T6...T1 Gb Zone 21, AEx/Ex tb IIIC T** °C Db | Cl.I, Zone 1, AEx/Ex ia IIC T6...T1 Gb Zone 21, AEx/ Ex ia tb IIIC T** °C Db |
| | CA, CC, HA, MC, RC, TA | Cl.I, Zone 1, AEx/Ex db ia [ia Ga] IIC T6...T1 Gb Zone 21, AEx/Ex tb [ia Da] IIIC T** °C Db | |

| Position | Order code for | Option selected | Description |
|----------|-----------------|-----------------|--------------------------------------|
| 4, 5 | Output, input 1 | BA | 4-20mA HART |
| | | CA | 4-20mA HART Ex-i passive |
| | | CC | 4-20mA HART Ex-i active |
| | | GA | PROFIBUS PA |
| | | HA | PROFIBUS PA Ex-i |
| | | LA | PROFIBUS DP |
| | | MA | Modbus RS485 |
| | | MB | Modbus TCP with Ethernet-APL |
| | | MC | Modbus TCP with Ethernet-APL Ex i |
| | | NA | EtherNet/IP 2-port switch integrated |
| | | RA | PROFINET IO 2-port switch integrated |

| Position | Order code for | Option selected | Description |
|----------|--------------------|-----------------|---|
| | | RB | PROFINET with Ethernet-APL |
| | | RC | PROFINET with Ethernet-APL Ex i |
| | | SA | FOUNDATION Fieldbus |
| | | TA | FOUNDATION Fieldbus Ex-i |
| 6 | Output, input 2 | A | W/o |
| | | B | 4-20mA |
| | | C | 4-20mA Ex-i passive |
| | | D | Configurable I/O initial setting off |
| | | E | Pulse/frequency/switch output |
| | | F | Pulse output, phase-shifted |
| | | G | Pulse/frequency/switch output Ex-i passive |
| | | H | Relay |
| | | I | 4-20mA input |
| | | J | Status input |
| 7 | Output, input 3 | A | W/o |
| | | B | 4-20mA |
| | | C | 4-20mA Ex-i passive |
| | | D | Configurable I/O initial setting off |
| | | E | Pulse/frequency/switch output |
| | | F | Pulse output, phase-shifted |
| | | G | Pulse/frequency/switch output Ex-i passive |
| | | H | Relay |
| | | I | 4-20mA input |
| | | J | Status input |
| 8 | Display; Operation | A | W/o; via communication |
| | | F | 4-line, illuminated; touch control |
| | | G | 4-line, illuminated; touch control + WLAN |
| | | M | Without; prepared for remote display DKX001 ¹⁾ |
| | | O | Separate, with remote display DKX001 ¹⁾ , 4-line, illuminated; 10 m / 30 ft cable; touch control |
| 9 | Housing | A | Alu, coated |
| | | L | Cast, stainless |

| Position | Order code for | Option selected | Description |
|----------|--|-----------------|--|
| 11, 12 | Meas. Tube Mat., Wetted Parts Surface | LA | Stainl. steel, cryogenic -196°C/-320°F |
| 17, 18 | Device Model | A1 | 1 |
| | | A2 | 2 |

1) DKX001 is separately approved.

Optional specifications

| ID | Order code for | Option selected | Description |
|----|-------------------|-----------------|---|
| Cx | Sensor option | CA | Rupture disk |
| Cx | Sensor option | CG | Extended neck for insulation |
| Cx | Sensor option | CH | Purge connection |
| Jx | Test, certificate | JP | Ambient temperature measuring device -50 °C |

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations or guidelines (e.g. CEC or NEC)
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application, and the temperature classes.
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- When using in hybrid mixtures (gas and dust occurring simultaneously), observe additional measures for explosion protection.

- Open the housing cover of the transmitter housing in explosion protection AEx/Ex db only if one of the following conditions is met:
 - An explosive atmosphere is not present.
 - A waiting time of 10 minutes is observed after switching off the power supply.

The following warning notice is on the device:
WARNING – AFTER DE-ENERGIZING, DELAY 10 MINUTES BEFORE OPENING ENCLOSURE IN TYPE OF PROTECTION EX D
- Observe all the technical data of the device (see nameplate).
- In devices with damaged AEx/Ex db threads:
 - Use in hazardous areas is not permitted.
 - Repair of AEx/Ex db threads is not permitted.
- Avoid electrostatic charge (e.g. caused by friction, cleaning, maintenance, strong currents in the medium):
 On the attached stainless steel nameplate and on painted metallic housings that are not integrated into the local potential equalization system.

⚠ WARNING

Substitution of components is not permitted.

- ▶ Substitution of components may impair intrinsic safety.

**Safety
instructions:
Installation**

- Continuous service temperature of the connecting cable:
 -40 to +80 °C (-50 to +80 °C for optional specification, ID Jx (Test, certificate) = JP); but at least according to the operating temperature range of the application plus allowance for process conditions ($T_{a, \min}$ and $T_{a, \max} + 20$ K).
- Only use certified cable glands suitable for the application. Observe national regulations and standards.
- The following applies when connecting the transmitter with a connection compartment in AEx/Ex db:

Only use separately certified cables and wire entries (AEx/Ex db IIC) which are suitable for operating temperatures up to 85 °C and for IP 66/67. If using conduit entries, the associated sealing mechanisms must be mounted directly on the housing.

Plastic sealing plugs act as transport protection and have to be replaced by suitable, individually approved installation material. The mounted metal thread extensions and blind plugs are tested and certified as part of the housing for type of protection AEx/Ex db IIC. The thread extension or the blind plug labeled as follows for identification purposes:
 d: NPT ½"

- The following applies when connecting the transmitter with a connection compartment in AEx/Ex eb:
Only use separately certified cable and wire entries and sealing plugs (AEx/Ex eb IIC) which are suitable for operating temperatures up to 85 °C and for IP 66/67. The cables must be routed such that they are securely seated, and sufficient strain relief must be ensured. The mounted metal thread extensions and blind plugs supplied are tested and certified as part of the housing for type of protection AEx/Ex eb IIC. Plastic sealing plugs act as transport protection and have to be replaced by suitable, individually approved installation material.
Supplied cable glands are separately certified and marked as components and meet device specification requirements.
- When the measuring device is connected, attention must be paid to the type of protection at the transmitter.
- Turning the transmitter housing
 - Loosen both hexagon socket screws until the transmitter housing can be turned.
 - Turn transmitter housing to desired position (mechanically limited); if necessary turn 270° in other direction.
 - Tighten both hexagon socket screws with a maximum of 7 Nm.
- In potentially explosive atmospheres:
 - Do not disconnect the electrical connection of the power supply circuit when energized.
 - Do not open the connection compartment cover when the device is energized.
Exception for the AEx/Ex eb connection compartment with intrinsically safe inputs and outputs: opening of the connection compartment is permitted for short period to perform live maintenance of intrinsically safe circuits. Internal non-intrinsically safe circuits are protected by an additional IP30 cover.
- Install the transmitter circuit wiring according to Canadian Electrical Code (CEC) respective National Electrical Code (NEC) using threaded conduit or other wiring methods in accordance with articles 500 to 510.
- When connecting through a conduit entry approved for this purpose, mount the associated sealing unit directly at the enclosure.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- Only use certified sealing plugs. The metal sealing plugs supplied meet this requirement.
- Transmitters with AEx/Ex db eb approval must not be connected via the service interface (CDI-RJ45)! Order code "Approval; Transmitter + Sensor", options (Ex de): C1, C2

Optional external WLAN antenna

- The external WLAN antenna can be used only in conjunction with an AEx/Ex eb connection compartment.
Use with an connection compartment is not permitted.
- Connect the antenna bushing H337 to the transmitter housing and tighten by hand.
- Use only external antennas supplied by Endress+Hauser.
- Connect antenna or antenna cable with plug-in connector type N (MIL-STD-348) to antenna bushing H337.

Intrinsic safety

- Observe the guidelines for interconnecting intrinsically safe circuits (e.g. , proof of intrinsic safety).
- When the intrinsically safe AEx/Ex ia circuits of the device are connected to certified intrinsically safe circuits of Category AEx/Ex ib for Equipment Groups IIC or IIB, the type of protection changes to AEx/Ex ib IIC or AEx/Ex ib IIB.
- The device can be connected to the remote display DKX001 which has IS explosion protection: refer to the Special documentation and Ex documentation.




- When using the remote display and operating module DKX001 the internal display and operating module must be removed.
- When using the separate approved, remote display and operating module DKX001, only use the following variants:
Basic specification of the remote display and operating module DKX001, order code "Approval", option CI

Potential equalization

- Integrate the device into the potential equalization .
- If the ground connection has been established via the pipe as specified, it is also possible to integrate the sensor into the potential equalization system via the pipe.
- The antenna bushing H337 of the external antenna must be integrated into the potential equalization system. This is the case if the sensor is connected in accordance with the regulations via the coupling.

Safety instructions: Zone 21

- To ensure dust-tightness, securely seal all housing openings, cable entries and sealing plugs.
- Only open all housing briefly, ensuring that no dust or moisture enters the housing.
- Only use certified cable entries. The metal cable entries, extensions and sealing plugs supplied meet this requirement.
- The metal extensions and blind plugs supplied are tested and certified as part of the enclosure for explosion protection. Plastic sealing plugs in extensions act as transport protection and have to be replaced by suitable, individually approved installation material. Supplied cable glands are separately certified and marked as components and meet device specification requirements.
- If the transmitter is connected to the remote display and operating module DKX001: Connection values →  28

Temperature tables

Ambient temperature

Minimum ambient temperature

- $T_{a, \min} = -40\text{ °C}$
- *Optional specification, ID Jx (Test, Certificate) = JP*
 $T_{a, \min} = -50\text{ °C}$ depending on the selected device variant (see nameplate)

Maximum ambient temperature

$T_{a, \max} = +60\text{ °C}$ depending on the medium temperature and temperature class.

Medium temperature

Minimum medium temperature

- Promass A, F, H, I, P, Q, S, X:
 $T_{m, \min} = -50\text{ °C}$
- Promass E, O:
 $T_{m, \min} = -40\text{ °C}$
- Promass F, Q with cryogenic temperature version (order code for "Measuring tube material", option LA):
 $T_{m, \min} = -196\text{ °C}$

Maximum medium temperature

- $T_{m, \max}$ for T6...T1 depending on the maximum ambient temperature $T_{a, \max}$.
- () = The maximum permitted medium temperatures in brackets only apply if the sensor is installed in such a way that the transmitter is not mounted above the sensor and free convection can occur on all sides.

Compact version**NOTICE****In case of heating, risk of overheating.**

- ▶ On devices with Heating jacket the corresponding temperature tables for isolated sensor, are to be observed.
- ▶ Make sure that the heating medium, may not exceeded the maximum specified medium temperature of the exact used temperature classes of the device.

Maximum medium temperature without thermal insulation according to Endress+Hauser specifications

*Promass A (8A3B**-*..., 8A3C**-*...)*

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|--------|--------------------------------|--------------------------|--------------------------|-------------|-------------|-------------|-------------|-------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 1 to 4 | 205 | 50 | 50 | 95 | 130 | 150 | 205 | 205 |
| | | 60 | - | 95 | 130 | 150 | 205 | 205 |

Promass E

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|---------|--------------------------------|--------------------------|--------------------------|-------------|-------------|-------------|-------------|-------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 to 50 | 150 | 50 | 50 | 100 | 130 | 130 | 150 | 150 |
| | | 55 | - | 80 | 100 | 130 | 150 | 150 |
| | | 60 | - | (80) | (100) | (130) | (150) | (150) |
| 80 | 150 | 50 | 50 | 75 | 110 | 150 | 150 | 150 |
| | | 55 | - | 75 | 110 | 150 | 150 | 150 |
| | | 60 | - | (75) | (110) | (150) | (150) | (150) |

Promass F

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----------|--|--------------------------|--------------------------|-------------|-------------|-------------|-------------|-------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 08 to 15 | 150 | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 60 | - | 95 | 130 | 150 | 150 | 150 |
| | 150 ²⁾ | 50 | 50 | 95 | 100 | 150 | 150 | 150 |
| | | 60 | - | 95 | 100 | 150 | 150 | 150 |

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|-----------|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| | 240 | 50 | 50 | 95 | 130 | 160 | 240 | 240 |
| | | 60 | – | 95 | 130 | 160 | (240) | (240) |
| 15 to 25 | 350 | 50 | 45 | 95 | 130 | 175 | 275 | 350 |
| | | 60 | – | 95 | 130 | 175 | 275 | 350 |
| 25 to 50 | 150 | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 60 | – | 95 | 130 | 150 | 150 | 150 |
| | 150 ²⁾ | 50 | 50 | 95 | 100 | 150 | 150 | 150 |
| | | 60 | – | 95 | 100 | 150 | 150 | 150 |
| | 240 | 50 | 50 | 95 | 130 | 160 | 240 | 240 |
| | | 60 | – | 95 | 130 | 160 | (240) | (240) |
| 80 to 250 | 150 | 50 | 50 | 75 | 110 | 150 | 150 | 150 |
| | | 60 | – | 75 | 110 | 150 | 150 | 150 |
| | 150 ²⁾ | 50 | 50 | 75 | 110 | 150 | 150 | 150 |
| | | 60 | – | 75 | 110 | 150 | 150 | 150 |
| | 240 | 50 | 50 | 75 | 110 | 170 | 240 | 240 |
| | | 60 | – | 75 | 110 | 170 | (240) | (240) |
| 50 to 250 | 350 | 50 | 45 | 85 | 120 | 175 | 275 | 350 |
| | | 60 | – | 85 | 120 | 175 | 275 | 350 |

- 1) Maximum temperature range, see nameplate
 2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass H

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----------|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 | 150 | 50 | 50 | 65 | 100 | 150 | 150 | 150 |
| | | 60 | – | 65 | 100 | 150 | 150 | 150 |
| 8 | 205 | 50 | 50 | 65 | 100 | 160 | 205 | 205 |
| | | 60 | – | 65 | 100 | 160 | 205 | 205 |
| 15 to 50 | 150 | 50 | 50 | 75 | 115 | 150 | 150 | 150 |
| | | 60 | – | 75 | 115 | 150 | 150 | 150 |

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----------|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 15 to 50 | 205 | 50 | 50 | 75 | 115 | 180 | 205 | 205 |
| | | 60 | - | 75 | 115 | 180 | 205 | 205 |

1) Maximum temperature range, see nameplate

Promass I

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|-----------------------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8, 15, 15FB, 25 | 150 | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 60 | - | 95 | 120 | (150) | (150) | (150) |
| 25FB, 40, 40FB, 50 | 150 | 50 | 50 | 85 | 120 | 150 | 150 | 150 |
| | | 60 | - | 85 | 120 | (150) | (150) | (150) |
| 50FB, 80 | 150 | 50 | 50 | 85 | 120 | 150 | 150 | 150 |
| | | 60 | - | 85 | 120 | (150) | (150) | (150) |
| FB = Full bore | | | | | | | | |

Promass O

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|-----------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 80 to 250 | 205 | 50 | 50 | 75 | 110 | 170 | 205 | 205 |
| | | 55 | - | 75 | 110 | 170 | 205 | 205 |
| | | 60 | - | 75 | 110 | 170 | (205) | (205) |

Promass P

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 | 150 | 45 | 45 | 65 | 100 | 150 | 150 | 150 |
| | | 60 | - | 65 | 100 | 150 | 150 | 150 |
| | 205 | 45 | 45 | 65 | 100 | 160 | 205 | 205 |
| | | 60 | - | 65 | 100 | 160 | 205 | 205 |

| DN | $T_{m, \max \text{ range}}^{1)}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|----------|--|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 15 to 50 | 150 | 50 | 50 | 75 | 115 | 150 | 150 | 150 |
| | | 60 | – | 75 | 115 | 150 | 150 | 150 |
| | 205 | 50 | 50 | 75 | 115 | 180 | 205 | 205 |
| | | 60 | – | 75 | 115 | 180 | 205 | 205 |

1) Maximum temperature range, see nameplate

Promass Q

| DN | $T_{m, \max \text{ range}}^{1)}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|-----------|--|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 25 to 250 | 205 | 50 | 50 | 75 | 110 | 160 | 205 | 205 |
| | | 60 | – | 75 | 110 | 160 | 205 | 205 |
| 25 to 250 | 150 ²⁾ | 50 | 50 | 75 | 110 | 150 | 150 | 150 |
| | | 60 | – | 75 | 110 | 150 | 150 | 150 |

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: $T_m = -196$ to 150 °C

Promass S

| DN | $T_{m, \max \text{ range}}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|----------|-------------------------------------|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 | 150 | 45 | 45 | 65 | 100 | 150 | 150 | 150 |
| | | 60 | – | 65 | 100 | 150 | 150 | 150 |
| 15 to 50 | 150 | 50 | 50 | 75 | 115 | 150 | 150 | 150 |
| | | 60 | – | 75 | 115 | 150 | 150 | 150 |

Promass X

| DN | $T_{m, \max \text{ range}}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|-----|-------------------------------------|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 350 | 180 | 50 | 50 | 90 | 120 | 170 | 180 | 180 |
| | | 55 | – | 90 | 120 | 170 | 180 | 180 |
| | | 60 | – | (90) | (120) | (170) | (180) | (180) |

Maximum medium temperature with thermal insulation according to Endress+Hauser specifications



For information on the thermal insulation of the device, see the "Thermal insulation" section of the "Operating instructions" document.

*Promass A (8A3B**-*..., 8A3C**-*...)*

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|--------|--------------------------------|--------------------------|--------------------------|-------------|-------------|-------------|-------------|-------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 1 to 4 | 205 | 50 | 50 | 95 | 130 | 150 | 205 | 205 |
| | | 55 | - | (95) | (130) | (150) | (205) | (205) |

Promass E

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|---------|--------------------------------|--------------------------|--------------------------|-------------|-------------|-------------|-------------|-------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 to 50 | 150 | 50 | 50 | 100 | 130 | 130 | 150 | 150 |
| | | 55 | - | (100) | (130) | (130) | (150) | (150) |
| 80 | 150 | 45 | 50 | 75 | 110 | 150 | 150 | 150 |
| | | 50 | - | 75 | 110 | 150 | 150 | 150 |
| | | 55 | - | (75) | (110) | (150) | (150) | (150) |

Promass F

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----------|--|--------------------------|--------------------------|-------------|-------------|-------------|-------------|-------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 08 to 15 | 150 | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 60 | - | 95 | 110 | (150) | (150) | (150) |
| | 150 ²⁾ | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 55 | - | 95 | (130) | (150) | (150) | (150) |
| | | 60 | - | 95 | 110 | 110 | 110 | 110 |
| | 240 | 50 | 50 | 95 | 130 | 160 | 240 | 240 |
| | | 55 | - | 95 | (130) | (160) | (240) | (240) |
| | | 60 | - | 95 | 110 | 110 | 110 | 110 |
| 15 to 25 | 350 | 50 | 45 | 95 | 130 | 175 | 275 | 350 |
| | | 60 | - | 95 | 130 | 175 | 275 | 350 |

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|-------------------|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 25 to 50 | 150 | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 60 | - | 95 | 110 | (150) | (150) | (150) |
| | 150 ²⁾ | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 55 | - | 95 | (130) | (150) | (150) | (150) |
| | | 60 | - | 95 | 110 | 110 | 110 | 110 |
| | 240 | 50 | 50 | 95 | 130 | 160 | 240 | 240 |
| | | 55 | - | 95 | (130) | (160) | (240) | (240) |
| | | 60 | - | 95 | 110 | 110 | 110 | 110 |
| | 80 to 250 | 150 | 50 | 50 | 75 | 110 | 150 | 150 |
| 60 | | | - | 75 | 110 | (150) | (150) | (150) |
| 150 ²⁾ | | 50 | 50 | 75 | 110 | 150 | 150 | 150 |
| | | 55 | - | 75 | 110 | 150 | 150 | 150 |
| | | 60 | - | 75 | 110 | 110 | 110 | 110 |
| 240 | | 50 | 50 | 75 | 110 | 170 | 240 | 240 |
| | | 55 | - | 75 | 110 | (170) | (240) | (240) |
| | | 60 | - | 75 | 110 | 110 | 110 | 110 |
| 50 to 250 | | 350 | 50 | 45 | 85 | 120 | 175 | 275 |
| | 60 | | - | 85 | 120 | 175 | 275 | 350 |

- 1) Maximum temperature range, see nameplate
2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass H

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----------|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 | 150 | 50 | 50 | 65 | 100 | 150 | 150 | 150 |
| | | 55 | - | 65 | 100 | (150) | (150) | (150) |
| | | 60 | - | 65 | 100 | 100 | 100 | 100 |
| 8 | 205 | 50 | 50 | 65 | 100 | 160 | 205 | 205 |
| | | 55 | - | 65 | 100 | (160) | (205) | (205) |
| | | 60 | - | 65 | 100 | 100 | 100 | 100 |
| 15 to 50 | 150 | 50 | 50 | 75 | 115 | 150 | 150 | 150 |

| DN | $T_{m, \max \text{ range}}^{1)}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|----------|--|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| | | 55 | – | 75 | 115 | (150) | (150) | (150) |
| | | 60 | – | 75 | 115 | 115 | 115 | 115 |
| 15 to 50 | 205 | 50 | 50 | 75 | 115 | 180 | 205 | 205 |
| | | 55 | – | 75 | 115 | (180) | (205) | (205) |
| | | 60 | – | 75 | 115 | 115 | 115 | 115 |

1) Maximum temperature range, see nameplate

Promass I

| DN | $T_{m, \max \text{ range}}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|-----------------------|-------------------------------------|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8, 15, 15FB, 25 | 150 | 50 | 50 | 95 | 130 | 150 | 150 | 150 |
| | | 60 | – | 95 | 120 | (150) | (150) | (150) |
| 25FB, 40, 40FB, 50 | 150 | 50 | 50 | 85 | 120 | 150 | 150 | 150 |
| | | 60 | – | 85 | 120 | (150) | (150) | (150) |
| 50FB, 80 | 150 | 50 | 50 | 85 | 120 | 150 | 150 | 150 |
| | | 60 | – | 85 | 120 | (150) | (150) | (150) |

FB = Full bore

Promass O

| DN | $T_{m, \max \text{ range}}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|-----------|-------------------------------------|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 80 to 250 | 205 | 50 | 50 | 75 | 110 | 170 | 205 | 205 |
| | | 55 | – | (75) | (110) | (170) | (205) | (205) |

Promass P

| DN | $T_{m, \max \text{ range}}^{1)}$ [°C] | $T_{a, \max}$ [°C] | $T_{m, \max}$ [°C] | | | | | |
|----|--|-----------------------|--------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 | 150 | 45 | 45 | 65 | 100 | 150 | 150 | 150 |
| | | 50 | – | 65 | 100 | 150 | 150 | 150 |

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----------|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| | 205 | 60 | - | 65 | 100 | 125 | (150) | (150) |
| | | 45 | 45 | 65 | 100 | 160 | 205 | 205 |
| | | 50 | - | 65 | 100 | 160 | 205 | 205 |
| | | 60 | - | 65 | 100 | 115 | (205) | (205) |
| 15 to 50 | 150 | 50 | 50 | 75 | 115 | 150 | 150 | 150 |
| | | 60 | - | 75 | 115 | 125 | (150) | (150) |
| | 205 | 50 | 50 | 75 | 115 | 180 | 205 | 205 |
| | | 60 | - | 75 | 115 | (150) | (150) | (150) |

1) Maximum temperature range, see nameplate

Promass Q

| DN | T _{m, max range} ¹⁾ [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|-----------|---|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 25 to 250 | 205 | 50 | 50 | 75 | 110 | 160 | 205 | 205 |
| | | 55 | - | (75) | (110) | (160) | (205) | (205) |
| 25 to 250 | 150 ²⁾ | 50 | 50 | 75 | 110 | 150 | 150 | 150 |
| | | 55 | - | (75) | (110) | (150) | (150) | (150) |

1) Maximum temperature range, see nameplate

2) Cryogenic temperature version: T_m = -196 to 150 °C

Promass S

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|----------|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 8 | 150 | 45 | 45 | 65 | 100 | 150 | 150 | 150 |
| | | 50 | - | 65 | 100 | 150 | 150 | 150 |
| | | 60 | - | 65 | 100 | 125 | (150) | (150) |
| 15 to 50 | 150 | 50 | 50 | 75 | 115 | 150 | 150 | 150 |
| | | 60 | - | 75 | 115 | 125 | (150) | (150) |


Promass X

| DN | T _{m, max range} [°C] | T _{a, max} [°C] | T _{m, max} [°C] | | | | | |
|-----|-----------------------------------|-----------------------------|--------------------------|----------------|----------------|----------------|----------------|----------------|
| | | | T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
| 350 | 180 | 50 | 50 | 90 | 120 | 170 | 180 | 180 |
| | | 55 | - | (90) | (120) | (170) | (180) | (180) |


With thermal insulation without Endress+Hauser specifications

The specified reference temperature T_{ref} and the maximum medium temperature $T_{m, max}$ for each temperature class must not be exceeded.

→  19



A0031198

 1 Position of reference point for temperature measurement

A Standard version

B Extended temperature version, cryogenic temperature version, high-temperature version

1 Reference point (T_{ref})

Reference temperature T_{ref}

| T6 [85 °C] | T5 [100 °C] | T4 [135 °C] | T3 [200 °C] | T2 [300 °C] | T1 [450 °C] |
|---------------|----------------|----------------|----------------|----------------|----------------|
| 59 | 72 | 75 | 76 | 77 | 77 |

Explosion hazards arising from gas and dust

Determining the temperature class and surface temperature with the temperature table

- In the case of gas: Determine the temperature class as a function of the maximum ambient temperature $T_{a, max}$ and the maximum medium temperature $T_{m, max}$.
- In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature $T_{a, max}$ and the maximum medium temperature $T_{m, max}$.

Example

- Measured maximum ambient temperature: $T_{a, max} = 47\text{ °C}$
- Measured maximum medium temperature: $T_{m, max} = 108\text{ °C}$

| | Ta [°C] | T6 [85°C] | T5 [100°C] | T4 [135°C] | T3 [200°C] | T2 [300°C] | T1 [450°C] |
|--|------------|--------------|---------------|---------------|---------------|---------------|---------------|
| | 35 | 50 | 85 | 120 | 140 | 140 | 140 |
| | 50 | - | 85 | 120 | 140 | 140 | 140 |
| | 60 | - | - | 120 | 140 | 140 | 140 |
| | 35 | 50 | 85 | 120 | 140 | 140 | 140 |
| | 45 | - | 85 | 120 | 140 | 140 | 140 |
| | 50 | - | - | 120 | 140 | 140 | 140 |

Diagram annotations: 1. points to the 50 in the last row, Ta column; 2. points to the 50 in the first row, Ta column; 3. points to the 120 in the last row, T4 column; 4. points to the 135°C in the T4 header.

A0031223

2 Procedure for determining the temperature class and surface temperature

1. Select device (optional).
2. In the column for the maximum ambient temperature $T_{a, \max}$ select the temperature that is immediately greater than or equal to the maximum ambient temperature $T_{a, \max}$ that is present.
 - ↳ $T_{a, \max} = 50^\circ\text{C}$.
The row showing the maximum medium temperature is determined.
3. Select the maximum medium temperature $T_{m, \max}$ of this row, which is immediately greater than or equal to the maximum medium temperature $T_{m, \max}$ that is present.
 - ↳ The column with the temperature class for gas is determined:
 $108^\circ\text{C} \leq 120^\circ\text{C} \rightarrow T_4$.
4. The maximum temperature of the temperature class determined corresponds to the maximum surface temperature for dust: $T_4 = 135^\circ\text{C}$.

Connection values: Signal circuits

The following tables contain specifications which are dependent on the transmitter type and its input and output assignment. Compare the following specifications with those on the nameplate of the transmitter.

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|--|-------|----------------|--------|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | 26 (+) | 27 (-) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

FOUNDATION Fieldbus

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|--|-------|----------------|--------|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | 26 (A) | 27 (B) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

PROFIBUS DP

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|--|-------|----------------|--------|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | 26 (B) | 27 (A) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

PROFIBUS PA

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|--|-------|----------------|--------|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | 26 (B) | 27 (A) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

Modbus RS485

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|--|-------|----------------|--------|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | 26 (B) | 27 (A) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

Modbus TCP with Ethernet-APL

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|--|-------|----------------|--------|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | 26 (+) | 27 (-) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

PROFINET

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|---|-------|------------------------------|--|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | PROFINET (RJ45 connector) | | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |


PROFINET with Ethernet-APL

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|--|-------|----------------|--------|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | 26 (+) | 27 (-) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

EtherNet/IP

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/output 3 | |
|---|-------|---------------------------------|--|----------------|--------|----------------|--------|
| 1 (+) | 2 (-) | EtherNet/IP (RJ45 connector) | | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Device-specific terminal assignment: adhesive label in terminal cover. | | | | | | | |

Remote display and operating module DKX001



A0027518

- 1 Remote display and operating module DKX001
- 2 Protective earth (PE)
- 3 Connecting cable
- 4 Measuring device
- 5 Protective earth (PE)

Safety-related values

| Order code "Output; input 1" | Output type | Safety-related values "Output; input 1" | |
|---------------------------------|-----------------------------------|---|--------|
| | | 26 (+) | 27 (-) |
| Option BA | Current output 4 to 20 mA HART | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | |
| Option GA | PROFIBUS PA | $U_N = 32 V_{DC}$ $U_M = 250 V_{AC}$ | |
| Option LA | PROFIBUS DP | $U_N = 32 V_{DC}$ $U_M = 250 V_{AC}$ | |
| Option MA | Modbus RS485 | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | |
| Option MB | Modbus TCP with Ethernet-APL | APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | |
| Option SA | FOUNDATION Fieldbus | $U_N = 32 V_{DC}$ $U_M = 250 V_{AC}$ | |
| Option NA | EtherNet/IP | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | |

| Order code "Output; input 1" | Output type | Safety-related values "Output; input 1" | |
|---------------------------------|----------------------------|---|--------|
| | | 26 (+) | 27 (-) |
| Option RA | PROFINET | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | |
| Option RB | PROFINET with Ethernet-APL | APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | |

| Order code "Output; input 2"; "Output; input 3" | Output type | Safety-related values | | | |
|---|-----------------------------------|--|--------|-----------------|--------|
| | | Output; input 2 | | Output; input 3 | |
| | | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Option B | Current output 4 to 20 mA | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | | | |
| Option D | User-configurable input/output | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | | | |
| Option E | Pulse/frequency/ switch output | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | | | |
| Option F | Double pulse output | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | | | |
| Option H | Relay output | $U_N = 30 V_{DC}$ $I_N = 100 mA_{DC}/500 mA_{AC}$ $U_M = 250 V_{AC}$ | | | |
| Option I | Current input 4 to 20 mA | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | | | |
| Option J | Status input | $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | | | |

Intrinsically safe values

| Order code for "Output; input 1" | Output type | Intrinsically safe values "Output; input 1" | |
|-------------------------------------|---|---|--------|
| | | 26 (+) | 27 (-) |
| Option CA | Current output 4-20mA HART Ex-i passive | $U_i = 30 \text{ V}$ $I_i = 100 \text{ mA}$ $P_i = 1.25 \text{ W}$ $L_i = 0 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$ | |
| Option CC | Current output 4-20mA HART Ex-i active | Ex ia $U_0 = 21.8 \text{ V}$ $I_0 = 90 \text{ mA}$ $P_0 = 491 \text{ mW}$ $L_0 = 4.1 \text{ mH(IIC)}/$ 15 mH(IIB) $C_0 = 160 \text{ nF(IIC)}/$ 1160 nF(IIB) $U_i = 30 \text{ V}$ $I_i = 10 \text{ mA}$ $P_i = 0.3 \text{ W}$ $L_i = 5 \text{ } \mu\text{H}$ $C_i = 6 \text{ nF}$ | |
| Option HA | PROFIBUS PA Ex i (STANDARD + FISCO) | Ex ia $U_i = 30 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8.5 \text{ W}$ $L_i = 10 \text{ } \mu\text{H}$ $C_i = 5 \text{ nF}$ | |

| Order code for "Output; input 1" | Output type | Intrinsically safe values "Output; input 1" | |
|----------------------------------|---|--|--------|
| | | 26 (+) | 27 (-) |
| Option MC | Modbus TCP with Ethernet-APL Ex i | 2-WISE power load, APL port profile SLAA¹⁾ Ex ia $U_i = 17.5 \text{ V}$ $I_i = 380 \text{ mA}$ $P_i = 5.32 \text{ W}$ $L_i = 10 \text{ }\mu\text{H}$ $C_i = 5 \text{ nF}$ Cable specifications according to 2-WISE: $R_c = 15 \text{ to } 150 \text{ }\Omega/\text{km}$ $L_c = 0.4 \text{ to } 1 \text{ mH/km}$ $C_c = 45 \text{ to } 200 \text{ nF/km}$ $C_c = C_c \text{ line/line} + 0,5 C_c \text{ line/screen}$, if both lines are floating, or $C_c = C_c \text{ line/line} + C_c \text{ line/screen}$, if the screen is connected to one line Length of cable (not including cable stubs) $\leq 200 \text{ m}$ (656.2) Length of cable stubs: $\leq 1 \text{ m}$ (3.3 ft) | |
| Option RC | PROFINET with Ethernet-APL Ex i | | |
| Option TA | FOUNDATION Fieldbus Ex i (STANDARD + FISCO) | Ex ia $U_i = 30 \text{ V}$ $I_i = 570 \text{ mA}$ $P_i = 8.5 \text{ W}$ $L_i = 10 \text{ }\mu\text{H}$ $C_i = 5 \text{ nF}$ | |

1) For further options see Ethernet-APL Installation Drawing HE_01622.

| Order code for "Output; input 2"; "Output; input 3" | Output type | Intrinsically safe values | | | |
|---|--|--|--------|-----------------|--------|
| | | Output; input 2 | | Output; input 3 | |
| | | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Option C | Current output 4 to 20 mA Ex i passive | $U_i = 30 \text{ V}$ $I_i = 100 \text{ mA}$ $P_i = 1.25 \text{ W}$ $L_i = 0$ $C_i = 0$ | | | |
| Option G | Pulse/frequency/switch output Ex i passive | $U_i = 30 \text{ V}$ $I_i = 100 \text{ mA}$ $P_i = 1.25 \text{ W}$ $L_i = 0$ $C_i = 0$ | | | |

Remote display DKX001

| Basic specification, position 1, 2 "Approval" | Terminal assignment | Basic specification, position 8 "Display; operation" Option O |
|--|---------------------|---|
| Option ¹⁾ C1, C2, C3, C4 | 81, 82, 83, 84 | A connecting cable with the value $L/R \leq 24 \mu\text{H}/\Omega$ and $C_{\text{cable}} \leq 1000 \text{ nF}$ must be used for the version for connecting to the remote display DKX001 or ODKX001. The cable supplied meets these requirements. |

1) If the DKX001 is ordered separately: CI



71648992

www.addresses.endress.com
