Technical Information **Deltabar S PMD75, FMD77, FMD78**

Differential pressure measurement and pressure measurement

Differential pressure transmitter with metallic measuring cells

Application

The device is used for the following measuring tasks:

- Flow measurement (volume flow or mass flow) in conjunction with primary devices in gases, vapors and liquids
- Level, volume or mass measurements in liquids
- High process temperatures up to 400 $^\circ C$ (752 $^\circ F) possible with diaphragm seal mount$
- Differential pressure monitoring, e.g. of filters and pumps

Your benefits

- Very good reproducibility and long-term stability
- High reference accuracy up to 0.035 %
- Turn down up to 100:1, higher on request
- Used for flow and differential pressure monitoring up to SIL3, certified to IEC 61508 by TÜV SÜD
- High level of safety during operation thanks to function monitoring from the measuring cell to the electronics
- The patented TempC membrane for the diaphragm seal reduces the measured error caused by environmental and process temperature effects to a minimum.
- Easy electronics replacement guaranteed with HistoROM[®]/M-DAT
- Cost-effective installation with Deltabar S FMD77, capillary on low-pressure side





Table of contents

About this document	4
Document function	4
Symbols used	
Documentation	
Terms and abbreviations	
Turn down calculation	
Registered trademarks	7
Function and system design	8
Device features	
Measuring principle	10
Product design	10
Communication protocol	11
Input	12
Measured variable	12
Measuring range	12
Output	14
Output signal	14
Signal range	14
Signal on alarm	14
Load	14
Damping	15
Alarm current	15 15
Firmware version	16
Wireless HART data	16
Protocol-specific data PROFIBUS PA	16
Protocol-specific data PROFIBUS PA	16 17
Protocol-specific data FOUNDATION Fieldbus	
Protocol-specific data FOUNDATION Fieldbus Power supply	17
Protocol-specific data FOUNDATION Fieldbus	17 20
Protocol-specific data FOUNDATION Fieldbus	17 20 20 21 21
Protocol-specific data FOUNDATION Fieldbus	17 20 20 21 21 21 21
Protocol-specific data FOUNDATION Fieldbus	17 20 20 21 21 21 21 22
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 21 21 22 22
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 21 21 22 22 22
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 21 22 22 22 23
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 21 21 22 22 22
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 21 22 22 22 23 23
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 21 22 22 22 23 23
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 21 22 22 22 23 23 23
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 22 22 22 23 23 23 23 23
Protocol-specific data FOUNDATION Fieldbus	17 20 21 21 22 22 22 23 23 23 23 23 23
Protocol-specific data FOUNDATION Fieldbus	17 20 20 21 21 22 22 23 23 23 23 23 23 23 23
Protocol-specific data FOUNDATION Fieldbus	17 20 20 21 21 22 22 22 23 23 23 23 23 23 23 23 23 23
Protocol-specific data FOUNDATION Fieldbus Power supply Terminal assignment Supply voltage Current consumption Electrical connection Terminals Cable entries Device plugs Cable specification Start-up current Residual ripple Overvoltage protection (optionally for HART, PROFIBUS PA and FOUNDATION Fieldbus) Influence of power supply Performance characteristics Response time Reference operating conditions Total performance Resolution	17 20 21 21 21 22 23 23 23 23 23 23 23 23 23
Protocol-specific data FOUNDATION Fieldbus Power supply Terminal assignment Supply voltage Current consumption Electrical connection Terminals Cable entries Device plugs Cable specification Start-up current Residual ripple Overvoltage protection (optionally for HART, PROFIBUS PA and FOUNDATION Fieldbus) Influence of power supply Performance characteristics Response time Reference operating conditions Total performance Resolution	17 20 21 21 21 22 22 23 23 23 23 23 23 23 23
Protocol-specific data FOUNDATION Fieldbus Power supply Terminal assignment Supply voltage Current consumption Electrical connection Terminals Cable entries Device plugs Cable specification Start-up current Residual ripple Overvoltage protection (optionally for HART, PROFIBUS PA and FOUNDATION Fieldbus) Influence of power supply Performance characteristics Response time Reference operating conditions Total performance Resolution Total error Long-term stability	17 20 21 21 21 22 22 23 23 23 23 23 23 23 23
Protocol-specific data FOUNDATION Fieldbus Power supply Terminal assignment Supply voltage Current consumption Electrical connection Terminals Cable entries Device plugs Cable specification Start-up current Residual ripple Overvoltage protection (optionally for HART, PROFIBUS PA and FOUNDATION Fieldbus) Influence of power supply Performance characteristics Response time Reference operating conditions Total performance Resolution	17 20 21 21 21 22 22 23 23 23 23 23 23 23 23

	34
Installation	34
Measuring arrangement	34
Measuring arrangement for devices with diaphragm seals	21
- FMD77 and FMD78	34
Orientation	34
Wall and pipe mounting, transmitter (optional)	35
Wall and pipe mounting, valve manifold (optional)	35
"Separate housing" version	36
Turning the housing	37
	וכ
Engineering	20
Environment	38
Ambient temperature range	38
Storage temperature range	39
Degree of protection	39
Climate class	39
Electromagnetic compatibility	39
Vibration resistance	39
Oxygen applications	40
Ultrapure gas applications	40
Hydrogen applications	40
Operation in very corrosive environment	40
D	
Process	41
Process temperature limits (temperature at transmitter)	41
Process temperature limits of capillary armoring: FMD77	
and FMD78	43
Process temperature range, seals	44 45
Pressure specifications	45
No. 1 to 1	
Mechanical construction	46
Device height	
	46
T14 housing, optional display on the side	47
T14 housing, optional display on the sideT15 housing, optional display on the top	47 48
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the side	47 48 48
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75	47 48 48 49
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75	47 48 48 49 50
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Process connections PMD75	47 48 48 49 50 51
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Process connections PMD75Valve manifold DA63M- (optional)	47 48 48 49 50
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillary	47 48 49 50 51 52
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillaryline	47 48 49 50 51 52 53
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - Overview	47 48 49 50 51 52
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high-	47 48 49 50 51 52 53 54
T14 housing, optional display on the side T15 housing, optional display on the top T17 housing (hygienic), optional display on the side Process connections PMD75 Process connections PMD75 Valve manifold DA63M- (optional) FMD77: Selecting the process connection and capillary line FMD77 - Overview . Process connections FMD77 with diaphragm seal, high- pressure side	47 48 49 50 51 52 53
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high-process connections FMD77 with diaphragm seal, high-	47 48 49 50 51 52 53 54 55
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm seal, high- pressure side	47 48 49 50 51 52 53 54 55 56
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFND77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm seal	47 48 49 50 51 52 53 54 55 55 56 57
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFND77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm seal	47 48 49 50 51 52 53 54 55 56 57 60
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm seal	47 48 49 50 51 52 53 54 55 55 56 57
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm seal	47 48 49 50 51 52 53 54 55 56 57 60 63
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high-pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm seal	47 48 49 50 51 52 53 54 55 56 57 60
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm se	47 48 49 50 51 52 53 54 55 56 57 60 63 63
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm seal	47 48 49 50 51 52 53 54 55 56 57 60 63 63 64
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD77 with diaphragm se	47 48 48 49 50 51 52 53 54 55 55 56 57 60 63 63 64 65
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD78 basic deviceProcess connections FMD78 with diaphragm seal	47 48 48 49 50 51 52 53 54 55 56 57 60 63 63 64 65 66
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD78 with diaphragm sealProcess connections FMD78 with diaphragm sealProcess connections FMD78 with diaphragm seal	47 48 49 50 51 52 53 54 55 56 57 60 63 63 64 65 66 68
T14 housing, optional display on the sideT15 housing, optional display on the topT17 housing (hygienic), optional display on the sideProcess connections PMD75Process connections PMD75Valve manifold DA63M- (optional)FMD77: Selecting the process connection and capillarylineFMD77 - OverviewProcess connections FMD77 with diaphragm seal, high- pressure sideProcess connections FMD77 with diaphragm sealProcess connections FMD78 basic deviceProcess connections FMD78 with diaphragm seal	47 48 48 49 50 51 52 53 54 55 56 57 60 63 63 64 65 66

Process connections FMD78 with diaphragm seal	75 77 78
Sonarato houging, Wall and nine mounting with mounting	80
Flushing rings 84 Weight 84 Materials not in contact with process 84	83 84 85 89 91

Operability	94
Operating concept	
Local operation	94
Remote operation	97
HistoROM [®] /M-DAT (optional)	99
System integration	99

Planning instructions for diaphragm seal

systems	100
Applications	100
Design and mode of operation	101
Differential pressure transmitter	102
Diaphragm seal filling oils	103
Operating temperature range	103
Response time	104
Cleaning instructions	104
Installation instructions	104
Vacuum applications	108

Certificates and approvals	109
CE mark	109
RCM-Tick marking	109
Ex approvals	109
EAC conformity	109
Suitable for hygiene applications	109
Certificate of current Good Manufacturing Practices	
(cGMP)	109
Functional safety SIL/ IEC 61508 Declaration of	
Conformity (optional)	109
Overfill prevention	109
CRN approval	109
Other standards and guidelines	110
Pressure Equipment Directive 2014/68/EU (PED)	110
Manufacturer declarations	111
Marine approval	111
Classification of process sealing between electrical	
systems and (flammable or combustible) process fluids in	
accordance with ANSI/ISA 12.27.01	111
Inspection certificate	111
Calibration	112
Service	112
Ordering information	113
Special device versions	113
Scope of delivery	113
Measuring point (TAG)	113
Configuration data sheet	114
5	
Accessories	118
HistoROM [®] /M-DAT	118
	110

Welding flanges and weld-in adapters	118
Manifolds	118
Additional mechanical accessories	118
Service-specific accessories	118
-	
Supplementary documentation	119
Field of Activities	119
Technical Information	119

	11/
Special Documentation	119
Operating Instructions	119
Brief Operating Instructions	119
Functional safety manual (SIL)	119
Overfill prevention	119
Safety Instructions (XA)	119
Installation/Control Drawings	120

About this document

Document function

The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.

Symbols used

Safety symbols

Symbol	Meaning
A DANGER	DANGER! This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.
WARNING	WARNING! This symbol alerts you to a dangerous situation. Failure to avoid this situation may result in serious or fatal injury.
	CAUTION! This symbol alerts you to a dangerous situation. Failure to avoid this situation may result in minor or moderate injury.
NOTICE	NOTE! This symbol contains information on procedures and other circumstances that do not result in personal injury.

Electrical symbols

Symbol	Meaning	Symbol	Meaning
	Protective ground connection A terminal that must be connected to ground prior to establishing any other connections.	4	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.

Symbols for certain types of Information

Symbol	Meaning
\checkmark	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
\mathbf{X}	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
Ĩ	Reference to documentation
	Reference to page
	Reference to graphic
	Visual inspection

Symbols in graphics

Symbol	Meaning
1, 2, 3	Item numbers
1. , 2. , 3	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections

Documentation

See the "Supplementary documentation" section \rightarrow 🗎 119



The document types listed are available: In the Download Area of the Endress+Hauser Internet site: www.endress.com \rightarrow Download


Safety Instructions (XA)

See the "Safety instructions" section \rightarrow 🗎 119


Terms and abbreviations 1 2 3 4 р 0 LRL LRV URV URL MWP OPL A0029505

Item	Term/abbreviation	Explanation	
1	OPL	The OPL (overpressure limit) for the measuring device depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to the measuring cell. Also observe pressure-temperature dependency. For the relevant standards and additional information, see the "Pressure specifications" section $\rightarrow \textcircled{B}$ 45. The OPL may only be applied for a limited period of time.	
2	MWP	The MWP (maximum working pressure) for the sensors depends on the lowest-rated element, with regard to pressure, of the selected components, i.e. the process connection has to be taken into consideration in addition to measuring cell. Also observe pressure-temperature dependency. For the relevant standards and additional information, see the "Pressure specifications" section $\rightarrow \textcircled{B} 45$. The maximum working pressure may be applied at the device for an unlimited period. The maximum working pressure can also be found on the nameplate.	
3	Maximum sensor measuring range	Span between LRL and URL This sensor measuring range is equivalent to the maximum calibratable/adjustable span.	
4	Calibrated/adjusted span	Span between LRV and URV Factory setting: 0 to URL Other calibrated spans can be ordered as customized spans.	
р	-	Pressure	
-	LRL	Lower range limit	
-	URL	Upper range limit	
-	LRV	Lower range value	
-	URV	Upper range value	
-	TD (turn down)	Turn down Example - see the following section.	

Turn down calculation



- Calibrated/adjusted span Zero point-based span URL sensor 1
- 2 3



Registered trademarks

Registered trademark of the FieldComm Group, Austin, USA

PROFIBUS®


Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

FOUNDATIONTM**Fieldbus**

Registered trademark of the FieldComm Group, Austin, Texas, USA

Function and system design

Device features



Field of application

PMD75:

- Flow
- Level
- Differential pressure
- Pressure
- FMD77:
- Level
- Differential pressure

FMD78:

- Level
- Differential pressure

Process connections

- PMD75:
- 1/4 18 NPT
- RC 1/4
- FMD77 low-pressure side (-):
- 1/4 18 NPT
- RC 1/4
- Alternatively available with capillary and diaphragm seal

FMD77 high-pressure side (+):

- EN DN 50 DN 100
- ASME NPS 2" 4"
- JIS 80A 100A

FMD78:

Wide range of diaphragm seals

Measuring ranges

- PMD75: from -10 to +10 mbar (-0.15 to +0.15 psi) to -40 to +40 bar (-600 to +600 psi)
 As gauge or absolute pressure sensor: up to 250 bar (3750 psi)
- FMD77: from -100 to +100 mbar (-1.5 to +1.5 psi) to -16 bar to +16 bar (-240 to +240 psi)
- FMD78: from -100 to +100 mbar (-1.5 to +1.5 psi) to -40 to +40 bar (-600 to +600 psi)

OPL

PMD75: on one side: up to 420 bar (6 300 psi) on both sides: up to 630 bar (9 450 psi) As gauge or absolute pressure sensor: up to 375 bar (5625 psi) FMD77: on one side: up to 160 bar (2 400 psi) on both sides: up to 240 bar (3 600 psi) FMD78: on one side: up to 160 bar (2 400 psi) on both sides: up to 240 bar (3 600 psi)

Process temperature range (temperature at process connection)

PMD75: -50 to +85 °C (-58 to +185 °F) -50 to +110 °C (-58 to +230 °F) at valve manifold (→ riangleq 41) FMD77: -70 to +400 °C (-94 to +752 °F) (depending on the filling oil) FMD78: -70 to +400 °C (-94 to +752 °F) (depending on the filling oil)

Ambient temperature range

- Without LCD display: up to -54 to +85 °C (-65 to +185 °F)
- With LCD display: -20 to +70 °C (-4 to +158 °F) (extended temperature application range -50 to +85 °C (-58 to +185 °F) with limitations in optical properties, such as display speed and contrast)
- Separate housing: -20 to +60 °C (-4 to +140 °F)
- Diaphragm seal systems depending on the version

Reference accuracy

- PMD75: up to ±0.035 % of the set span
- FMD77: up to ±0.075 % of the set span
- FMD78: up to ±0.075 % of the set span

Supply voltage

Supply voltage non-Ex

- 4 to 20 mA HART: 10.5 to 45 V DC
- PROFIBUS PA and FOUNDATION Fieldbus: 9 to 32 V DC

Supply voltage Ex ia

10.5 to 30 V DC

Output

4 to 20 mA with superimposed HART protocol, PROFIBUS PA or FOUNDATION Fieldbus

Options

- HistoROM[®]/M-DAT memory chip
- PMD75: with blind flange on LP side for gauge and absolute pressure measurement


Specialties

PMD75:

p_{stat} up to 420 bar (6 300 psi)
 Process isolating diaphragm: tantalum
 FMD77:
 For high medium temperatures
 FMD78:
 For high medium temperatures
 Wide range of diaphragm seals

Measuring principle

Metal process isolating diaphragm



- 1 Measuring element
- 2 Middle diaphragm
- 3 Filling oil
- 4 Process isolating diaphragm


The process isolating diaphragms are deflected on both sides by the acting pressures. A filling oil transfers the pressure to a resistance bridge (semiconductor technology). The change in the bridge output voltage, which depends on the differential pressure, is measured and processed

Advantages:

- Standard system pressures: 160 bar (2 400 psi) up to 420 bar (6 300 psi)
- High long-term stability
- Very high single-sided overload resistance

Product design

Level measurement (level, volume and mass):




- A Level measurement with FMD77
- *B Level measurement with FMD78*
- h Height (level)
- Δp Differential pressure
- ρ Density of the medium
- g Gravitation constant

Your benefits

- Selection of the level operating mode which is optimum for your application in the device software
- Volume and mass measurements in any vessel shape by means of a freely programmable characteristic curve
- Choice of diverse level units with automatic unit conversion
- A customized unit can be specified
- Has a wide range of uses, e.g.
 - for level measurement in vessels with pressure overlay
 - for foam formation
 - in vessels with agitators of screen fittings
 - for liquid gases
 - for standard level measurement

Flow measurement

Flow measurement with Deltabar S and primary device:



A Orifice plate

- B Pitot tube
- Q Flow
- Δp Differential pressure, $\Delta p = p_1 p_2$

Your benefits

- Choice of four flow modes of operation: volume flow, corrected volume flow (European norm conditions), standard volume flow (American standard conditions) and mass flow
- Choice of diverse flow units with automatic unit conversion
- A customized unit can be specified
- Low flow cut off: when activated, this function suppresses small flows which can lead to large fluctuations in the measured value.
- Contains two totalizers as standard. One totalizer can be reset to zero.
- The totalizing mode and unit can be individually set for each totalizer. This allows independent daily and annual quantity totalizing.

Communication protocol	 4 to 20 mA with HART communication protocol PROFIBUS PA Endress+Hauser devices meet the requirements specified by the FISCO model. Due to a low current consumption of 13 mA ± 1 mA, the following number of devices can be operated on one bus segment if installing as per FISCO: up to 7 devices for Ex ia, CSA IS and FM IS applications or up to 27 devices for all other applications e.g. in non-hazardous areas, Ex nA etc. Further information on PROFIBUS PA can be found in Operating Instructions BA00034S "PROFIBUS DP/PA: Guidelines for planning and commissioning" and in the PNO Guideline. FOUNDATION Fieldbus Endress+Hauser devices meet the requirements specified by the FISCO model.
	 Due to a low current consumption of 15.5 mA ± 1 mA, the following number of devices can be operated on one bus segment if installing as per FISCO: up to 6 devices for Ex ia, CSA IS and FM IS applications or up to 24 devices for all other applications e.g. in non-hazardous areas, Ex nA etc. Further information on FOUNDATION Fieldbus, such as requirements for bus system components, can be found in Operating Instructions BA00013S "FOUNDATION Fieldbus Overview".

Input

Measured variable

Measured process variables

Differential pressure, pressure

Calculated process variables

- Flow rate (volume flow or mass flow)
- Absolute pressure, gauge pressure
- Level (level, volume or mass)

Measuring range

Sensor	Maximum sensor measuring range		Smallest calibratable span ¹⁾	MWP	OPL		Min. static pressure ²⁾	Option ³⁾		
	lower (LRL)	upper (URL)	-		on one side	on both sides		PN 160		
[mbar (psi)]	[mbar (psi)]	[mbar (psi)]	[mbar (psi)]	[bar (psi)]	[bar (psi)]	[bar (psi)]	[mbar _{abs} (psi _{abs})]			
FMD77, FMD7	78, PMD75: Opt	ion PN 160 / 10	5 MPa / 2400 psi	1			1			
10 (0.15) (PMD75 only)	-10 (-0.15)	+10 (+0.15)	0.25 (0.00375)	160 (2400)	160 (2400)	240 (3600)		7B		
30 (0.45) (PMD75 only)	-30 (-0.45)	+30 (+0.45)	0.3 (0.0045)	160 (2400) 160 (2400) ⁵⁾ "+" side ⁶⁾ : 160 (2400) ⁵⁾			0.1 (0.0015)	7C		
100 (1.5)	-100 (-1.5)	+100 (+1.5)	1/5 (0.015/0.075) ⁴⁾					7D		
500 (7.5)	-500 (-7.5)	+500 (+7.5)	5 (0.075)					7F		
3000 (45)	-3000 (-45)	+3000 (+45)	30 (0.45)					7H		
16000 (240)	-16000 (-240)	+16000 (+240)	160 (2.4)				7L			
40000 (600)	-40000 (-600)	+40000 (+600)	400 (6)					7M		
PMD75: Optio	on PN 420 / 42 I	MPa / 6300 psi		1				, I		
100 (1.5)	-100 (-1.5)	+100 (+1.5)	1/5 (0.015/0.075) ⁴⁾	420 (6300) ^{7) 8)}	420 (6300)	630 (9450)		8D		
500 (7.5)	-500 (-7.5)	+500 (+7.5)	5 (0.075)	-				8F		
3000 (45)	-3000 (-45)	+3000 (+45)	30 (0.45)	1			0.1 (0.0015)	8H		
16000 (240)	-16000 (-240)	+16000 (+240)	160 (2.4)	1					0.1 (0.0015)	8L
40000 (600)	-40000 (-600)	+40000 (+600)	400 (6)	420 (6300) ^{7) 5) 8)}	"+" side ⁶⁾ : 420 (6300)			8M		

1) Turndown > 100:1 on request

2) The minimum static pressure indicated in the table applies to silicone oil under reference operating conditions. Min. static pressure at 85 °C (185 °F) for silicone oil: up to 10 mbar_{abs} (0.15 psi_{abs}). FMD77 and FMD78: Min. static pressure: 50 mbar_{abs} (0.75 psi_{abs}); pay attention to the pressure and temperature operating limits of the selected fill fluid $\rightarrow \cong$ 103. For vacuum applications, pay attention to the installation instructions $\rightarrow \cong$ 108.

3) Product Configurator, order code for "Nominal range; PN"

4) Smallest calibratable span for the PMD75: 1 mbar (0.015 psi); smallest calibratable span for the FMD77 and FMD78: 5 mbar (0.075 psi)

5) When pressure is applied on the negative side only, the MWP is 100 bar (1500 psi).

6) "–" side: 100 bar (1500 psi)

7) If CRN approval is selected, the following limited MWP values apply (MWP values refer to the maximum temperature of the device): without side vent valves: 262 bar (3 800 psi); with side vent: 179 bar (2 596.2 psi); with copper seals: 124 bar (1798.5 psi).

8) MWP on both sides only.

Sensor	Maximum sensor measuring range		Smallest calibratable span	MWP	OPL		Min. static pressure ¹⁾	Option ²⁾
	lower (LRL)	upper (URL)			on one side	on both sides		
bar (psi)	bar (psi)	bar (psi)	bar (psi)	bar (psi)	bar (psi)		mbar _{abs} (psi _{abs})	
PMD75: optiona	PMD75: optionally available as a gauge or absolute pressure sensor							
160 (2400) gauge	-1 (-15)	160 (2400)	40 (600)	160 (2400)	240 (3600)	_ 3)	10	7Q
160 (2400) abs	0	160 (2400)	4 (60)	160 (2400)	240 (3600)	_ 3)	10	7V
250 (3750) gauge	-1 (-15)	250 (3750)	40 (600)	250 (3750)	375 (5625)	_ 3)	10	7R ⁴⁾
250 (3750) abs	0	250 (3750)	4 (60)	250 (3750)	375 (5625)	_ 3)	10	7W ⁴⁾

The minimum static pressure indicated in the table applies to silicone oil under reference operating conditions. Min. static pressure at 85 °C (185 °F) for silicone oil: up to 10 mbar_{abs} (0.15 psi_{abs}). 1)

Product Configurator, order code for "Nominal range; PN" Available only with blind flange on LP side. 2)

3)

4) The 250 bar sensor can be used over the entire measuring range with up to 100,000 load changes without specification restrictions.

Output signal

- 4 to 20 mA with superimposed digital communication protocol HART, 2-wire
- Digital communication signal PROFIBUS PA (Profile 3.0), 2-wire
 Signal coding: Manchester Bus Powered (MBP): Manchester II
 - Transmission rate: 31.25 KBit/s voltage mode
- Digital communication signal FOUNDATION Fieldbus, 2-wire
 - Signal coding: Manchester Bus Powered (MBP): Manchester II
 - Transmission rate: 31.25 KBit/s voltage mode

Output	Internal + LCD	External + LCD	Internal	
			A0021280	
		Option ¹⁾		
4 to 20mA HART	В	А	С	
4 to 20mA HART, Li=0	Е	D	F	
PROFIBUS PA	N	М	0	
FOUNDATION Fieldbus	Q	Р	R	

1) Product Configurator, order code for "Display, operation: "

Signal range	4 to 20 mA
	3.8 mA to 20.5 mA
Signal on alarm	4 to 20 mA HART
	As per NAMUR NE43.
	 Max. alarm: can be set from 21 to 23 mA (factory setting: 22 mA) Hold measured value: last measured value is held Min. alarm: 3.6 mA
	PROFIBUS PA
	As per NAMUR NE43.
	Can be set in the Analog Input Block.

Options:

- Last Valid Out Value (factory setting)
- Fail Safe Value
- Status bad

FOUNDATION Fieldbus

As per NAMUR NE43.

Can be set in the Analog Input Block.


Options:

- Last Good Value
- Fail Safe Value (factory setting)
- Wrong Value

Load

4 to 20 mA HART

In order to guarantee sufficient terminal voltage in two-wire devices, a maximum load resistance R (including line resistance) must not be exceeded depending on the supply voltage U_0 of the supply unit. In the following load diagrams, observe the position of the jumper and the explosion protection:



Designation	Option 1
02.20.zz, HART 7, DevRev22	72
02.11.zz, HART 5, DevRev21	73
04.00.zz, FF, DevRev07	74
04.01.zz, PROFIBUS PA, DevRev03	75
02.10.zz, HART 5, DevRev21	76
03.00.zz, FF, DevRev06	77

Designation	Option ¹⁾
04.00.zz, PROFIBUS PA	78
02.30.zz, HART 7	71

1) Product Configurator, order code for "Firmware version"

Protocol-specific data HART	Manufacturer ID	17 (11 hex)
	Device type ID	23 (17 hex)
	Device revision	 21 (15 hex) - SW version 02.1y.zz - HART specification 5 22 (16 hex) - SW version 02.2y.zz - HART specification 7
	HART specification	• 5 • 7
	DD revision	 4 (Russian in language selection) for device revision 21 3 (Dutch in language selection) for device revision 21 1 for device revision 22
	Device description files (DTM, DD)	Information and files under:
		www.endress.comwww.fieldcommgroup.org
	HART load	Min. 250 Ω
	HART device variables	The measured values are assigned to the device variables as follows:
		Measured values for PV (primary variable) Pressure Flow Level Tank content
		Measured values for SV, TV (second and third variable) Pressure Totalizer
		Measured values for QV (fourth variable) Temperature
	Supported functions	 Burst mode Additional transmitter status Device locking Alternative measuring modes

	Wire	less	HA	RT	data
--	------	------	----	----	------

Minimum starting voltage	11.5 V (default) or 10.5 V if jumper not set to "Test" position $^{1)}$
Start-up current	12 mA
Starting time	10 s
Minimum operating voltage	11.5 V (default) or 10.5 V if jumper not set to "Test" position $^{1)}$
Multidrop current	4 mA
Time for connection setup	1 s

1) Or higher if operating near the ambient temperature limits (–40 to +85 $^{\circ}$ C (–40 to +185))

Protocol-specific data PROFIBUS PA	Manufacturer ID	17 (11 hex)
	Identification number	1542 hex
	Profile version	 3.0 SW version 03.00.zz SW version 04.00.zz 3.02 SW version 04.01.zz (device revision 3) Compatibility with SW version 03.00.zz and higher.
	GSD revision	4 (SW version 3.00.zz and 4.00.zz)5 (device revision 3)

DD revision	1 (SW version 3.00.zz and 4.00.zz)1 (device revision 3)
GSD file	Information and files under:
DD files	www.endress.comwww.profibus.org
Output values	Measured values for PV (via Analog Input Function Block) Pressure Level Flow Tank content Measured values for SV Pressure Temperature Measured value for QV Totalizer
Input values	Input value sent from PLC, can be shown on display
Supported functions	 Identification & maintenance, simplest device identifier on the control system and nameplate Condensed status (only with Profile Version 3.02) Automatic ID number adjustment and switchable to the following ID numbers (only with Profile Version 3.02): 9700: Profile-specific transmitter identification number with the "Classic" or "Condensed" status. 1504: Compatibility mode for the old Deltabar S generation (FMD230, FMD630, FMD633, PMD230, PMD235). 1542: Identification number of the new Deltabar S generation (FMD77, FMD78, PMD75). Device locking: The device can be locked by hardware or software.

Protocol-specific data FOUNDATION Fieldbus

Manufacturer ID	452B48 hex
Device type	1009 hex
Device revision	 6 - SW version 03.00.zz 7 - SW version 04.00.zz (FF-912)
DD revision	 3 (device revision 6) 2 (device revision 7)
CFF revision	 4 (device revision 6) 1 (device revision 7)
DD files	Information and files under:
CFF files	www.endress.comwww.fieldcommgroup.org
Device tester version (ITK version)	 5.0 (device revision 6) 6.01 (device revision 7)
Number of ITK test campaign	 IT054700 (Device Revision 6) IT085400 (Device Revision 7)
Link-Master (LAS) capable	Yes
Choice of "Link Master" and "Basic Device"	Yes; Factory setting: Basic Device
Node address	Factory setting: 247 (F7 hex)
Supported functions	Field diagnostics profile (only with FF912)
	The following methods are supported: • Reboot • Configure error as warning or alarm • HistoROM • Peakhold • Alarm info • Sensor trim

Number of VCRs	44 (device revision 6)24 (device revision 7)
Number of Link Objects in VFD	50

Virtual communication references (VCRs)

	Device revision 6	Device revision 7
Permanent Entries	44	1
Client VCRs	0	0
Server VCRs	5	10
Source VCRs	8	43
Sink VCRs	0	0
Subscriber VCRs	12	43
Publisher VCRs	19	43

Link settings

	Device revision 6	Device revision 7
Slot time	4	4
Min. Inter PDU delay	12	10
Max. response delay	10	10

Transducer Blocks

Block	Contents	Output values	
TRD1 Block	Contains all parameters related to the measurement	Pressure, flow or level (channel 1)Process temperature (channel 2)	
Service Block	Contains service information	 Pressure after damping (channel 3) Pressure peakhold indicator (channel 4) Counter for max. pressure transgressions (channel 5) 	
Dp Flow Block	Contains flow and totalizer parameters	Totalizer 1 (channel 6)	
Diagnostic block	Contains diagnostic information	Error code via DI channels (channel 0 to 16)	
Display block	Contains parameters to configure the onsite display	No output values	

Function blocks

Block	Contents	Number	Execution time		Functionality	
		Blocks	Device Revision 6	Device Revision 7	Device Revision 6	Device Revision 7
Resource Block	The Resource Block contains all the data that uniquely identify the device. It is an electronic version of a nameplate of the device.	1			enhanced	enhanced
Analog Input Block 1 Analog Input Block 2 Analog Input Block 3	The AI Block receives the measuring data from the Sensor Block, (selectable via a channel number) and makes the data available to other function blocks at its output. Enhancement: Digital outputs for process alarms, fail safe mode	3	45 ms	45 ms (without trend and alarm reports)	enhanced	enhanced
Digital Input Block	This block contains the discrete data of the Diagnose Block (selectable via a channel number 0 to 16) and provides them for other blocks at the output.	1	40 ms	30 ms	standard	enhanced
Digital Output Block	This block converts the discrete input and thus initiates an action (selectable via a channel number) in the DP Flow Block or in the Service Block. Channel 1 resets the counter for max. pressure transgressions.	1	60 ms	40 ms	standard	enhanced
PID Block	This block is used as a proportional-integral-derivative controller and can be used universally for closed-loop-control in the field. It enables cascade mode and feedforward control. Input IN can be indicated on the display. The selection is performed in the Display Block (DISPLAY_MAIN_LINE_CONTENT).	1	120 ms	70 ms	standard	enhanced
Arithmetic Block	This block is designed to permit simple use of popular measurement math functions. The user does not have to know how to write equations. The math algorithm is selected by name, chosen by the user for the function to be performed.	1	50 ms	40 ms	standard	enhanced
Input Selector Block	The Input Selector Block facilitates the selection of up to four inputs and generates an output based on the configured action. This block normally receives its inputs from AI Blocks. The block enables the selection of maximum, minimum, average and 'first good' values. Inputs IN1 to IN4 can be shown on the display. The selection is performed in the Display Block (DISPLAY_MAIN_LINE_CONTENT).	1	35 ms	35 ms	standard	enhanced
Signal Characterizer Block	The Signal Characterizer Block has two sections, each with an output value that is a non-linear function of the input value. The non-linear function is generated by a single look-up table with 21 arbitrary x-y pairs.	1	30 ms	40 ms	standard	enhanced
Integrator Block	The Integrator Block integrates a variable as a function of the time or accumulates the counts from a Pulse Input Block. The block may be used as a totalizer that counts up until reset or as a batch totalizer that has a setpoint, where the integrated or accumulated value is compared to pre-trip and trip settings, generating a binary signal when the setpoint is reached.	1	35 ms	40 ms	standard	enhanced
Analog Alarm Block	This block contains all process alarm conditions (working like a comparator) and represents them at the output.	1	35 ms	35 ms	standard	enhanced

Additional function block information:

Instantiate F	Function Block	YES	YES
Number of a	dditional instantiatable function blocks	9	4

Power supply


WARNING

Electrical safety is compromised by an incorrect connection!

- All explosion protection data are given in separate Ex documentation which is available upon request. The Ex documentation is supplied as standard with all devices approved for use in explosion hazardous areas →
 119.
- Devices with integrated overvoltage protection must be grounded $\rightarrow \square 23$.
- Protective circuits against reverse polarity, HF influences and overvoltage peaks are integrated.


Terminal assignment

4 to 20 mA HART



- 1 Housing
- 2 Supply voltage
- 3 4 to 20 mA
- 4 Devices with integrated overvoltage protection are labeled "OVP" (overvoltage protection) here.
- 5 External ground terminal
- 6 4 to 20 mA test signal between positive and test terminal
- 7 Internal ground terminal
- 8 Jumper for 4 to 20 mA test signal $\rightarrow \cong 21$

PROFIBUS PA and FOUNDATION Fieldbus



- 1 Housing
- 2 Supply voltage
- 3 Devices with integrated overvoltage protection are labeled "OVP" (overvoltage protection) here.
- 4 External ground terminal
- 5 Internal ground terminal

Supply voltage

4 to 20 mA HART

Electronic version	Jumper for 4 to 20 mA test signal in "Test" position (delivery status)	Jumper for 4 to 20 mA test signal in "Non-test" position
Version for non-hazardous area	11.5 to 45 V DC	10.5 to 45 V DC
Intrinsically safe	11.5 to 30 V DC	10.5 to 30 V DC
Other types of protectionDevices without a certificate	11.5 to 45 V DC (Versions with 35 V DC plug-in connector)	10.5 to 45 V DC (Versions with 35 V DC plug-in connector)

Measuring a 4 to 20 mA test signal

Jumper position for test signal	Description
Test ✓ → → →	 Measurement of 4 to 20 mA test signal via the positive and test terminal: possible. (Thus, the output current can be measured without interruption via the diode.) As-delivered state Minimum supply voltage: 11.5 V DC
Test ✓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓ ↓	 Measurement of 4 to 20 mA test signal via the positive and test terminal: not possible. Minimum supply voltage: 10.5 V DC

PROFIBUS PA

Version for non-hazardous areas: 9 to 32 V DC

• Ex ia:

- Installation in bus system according to FISCO model: Ui=17.5 V DC
- Point-to-point installation: Ui = 24 V DC

FOUNDATION Fieldbus

Version for non-hazardous areas: 9 to 32 V DC

Ex ia:

- Installation in bus system according to FISCO model: Ui=17.5 V DC
- Point-to-point installation: Ui = 24 V DC

 Current consumption
 • PROFIBUS PA: 13 mA ±1 mA, switch-on current corresponds to IEC 61158-2, Clause 21

 • FOUNDATION Fieldbus: 15.5 mA ±1 mA, switch-on current corresponds to IEC 61158-2, Clause 21

 Electrical connection
 PROFIBUS PA

 The digital communication signal is transmitted to the bus via a two-wire connection. The bus also provides the power supply. For further information on the network structure and grounding and for further bus system components such as bus cables, see the relevant documentation, e.g. Operating Instructions BA00034S "PROFIBUS DP/PA: Guidelines for planning and commissioning" and the PNO

FOUNDATION Fieldbus

Guideline.

The digital communication signal is transmitted to the bus via a two-wire connection. The bus also provides the power supply. For further information on the network structure and grounding and for further bus system components such as bus cables, see the relevant documentation, e.g. Operating Instructions BA00013S "FOUNDATION Fieldbus Overview" and the FOUNDATION Fieldbus Guideline.

Terminals

• Supply voltage and internal ground terminal: 0.5 to 2.5 mm² (20 to 14 AWG)

- External ground terminal: 0.5 to 4 $\rm mm^2$ (20 to 12 AWG)


Cable entries

Approval	Cable gland	Clamping range
Standard, II 1/2 G Ex ia, IS	Plastic M20x1.5	5 to 10 mm (0.2 to 0.39 in)
ATEX II 1/2 D, II 1/3 D, II 1/2 GD Ex ia, II 1 GD Ex ia, II 3 G Ex nA	Metal M20x1.5 (Ex e)	7 to 10.5 mm (0.28 to 0.41 in)

For additional technical data, see section on housing \rightarrow \cong 47

Device plugs


Connection for devices with Harting plug Han7D



- A Electrical connection for devices with Harting plug Han7D
- *B* View of plug-in connection on the device
- Brown
- ≟ Green/yellow
- + Blue

Material: CuZn, gold-plated plug-in jack and plug contacts

Connection of devices with M12 plug



- 1 Signal +
- 2 Not assigned
- 3 Signal –
- 4 Ground

Endress+Hauser offers the following accessories for devices with an M12 plug:

Plug-in jack M 12x1, straight

- Material: body PA; union nut CuZn, nickel-plated
- Degree of protection (fully locked): IP67
- Order number: 52006263


Plug-in jack M 12x1, elbowed

- Material: body PBT/PA; union nut GD-Zn, nickel-plated
- Degree of protection (fully locked): IP67
- Order number: 71114212

Cable $4x0.34 \text{ mm}^2$ (20 AWG) with M12 elbowed socket, screw plug, length 5 m (16 ft)

- Material: body PUR; union nut CuSn/Ni; cable PVC
- Degree of protection (fully locked): IP67
- Order number: 52010285

Connection of devices with 7/8" plug



Response time					
	 Acyclic: min. 330 ms, typically 590 ms (depending on command # and number of preambles) Cyclic (burst): min. 160 ms, typically 350 ms (depending on command # and number of preambles) 				
	PROFIBUS PA				
	 Acyclic: approx. 60 ms to 70 ms (depending on Min. Slave Interval) Cyclic: approx. 10 ms to 13 ms (depending on Min. Slave Interval) 				
	FOUNDATION Fieldbus				
	 Acyclic: typically 100 ms (for standard bus parameter settings) Cyclic: max. 20 ms (for standard bus parameter settings) 				
Reference operating conditions	• As per IEC 62828-2 / IEC 60770 • Ambient temperature T_A = constant, in the range of +22 to +28 °C (+72 to +82 °F) • Humidity φ = constant, in the range of: 5 to 80 % rF ± 5 % • Atmospheric pressure p_A = constant, in the range of: 860 to 1060 mbar (12.47 to 15.37 psi) • Position of the measuring cell: horizontal ±1° • Input of LOW SENSOR TRIM and HIGH SENSOR TRIM for lower range value and upper range value • Zero based span • Membrane material for PMD75: AISI 316L (1.4435), Alloy C276, gold/rhodium-coated, Monel • Membrane material for FMD77, FMD78: AISI 316L (1.4435) • Fill fluid: silicone oil • Supply voltage: 24 V DC ±3 V DC • Load with HART: 250 φ • Turn down (TD) = URL/ URV - LRV				
Total performance	The performance characteristics refer to the accuracy of the device. The factors that influence the accuracy can be divided into two groups Total performance of device Installation factors 				
	All of the performance characteristics meet the requirement of $\geq \pm 3$ sigma.				
	The total performance of the device comprises the reference accuracy and the ambient temperature effect and is calculated using the following formula:				
	Total performance = $\pm \sqrt{((E1)^2 + (E2)^2 + (E3)^2)}$				
	E1 = Reference accuracy				
	-				
	E1 = Reference accuracy				
	E1 = Reference accuracy E2 = Ambient temperature effect				
	E1 = Reference accuracy E2 = Ambient temperature effect E3 = Static pressure effect				
	E1 = Reference accuracy E2 = Ambient temperature effect E3 = Static pressure effect Calculation of E2:				
	E1 = Reference accuracy E2 = Ambient temperature effect E3 = Static pressure effect Calculation of E2: Ambient temperature effect per ± 28 °C (50 °F) (Corresponds to a range of -3 to ± 53 °C (± 27 to ± 127 °F)) E2 = E2 _M + E2 _E				
	E1 = Reference accuracy E2 = Ambient temperature effect E3 = Static pressure effect Calculation of E2: Ambient temperature effect per ± 28 °C (50 °F) (Corresponds to a range of -3 to ± 53 °C (± 27 to ± 127 °F)) E2 = E2 _M + E2 _E E2 _M = Main temperature error				
	E1 = Reference accuracy E2 = Ambient temperature effect E3 = Static pressure effect Calculation of E2: Ambient temperature effect per ± 28 °C (50 °F) (Corresponds to a range of -3 to ± 53 °C (± 27 to ± 127 °F)) E2 = E2 _M + E2 _E				

Performance characteristics

HART

Response time

Calculation of the total performance with the Endress+Hauser Applicator

Detailed inaccuracies, e.g. for other temperature ranges, can be calculated with the Applicator "Sizing Pressure Performance".



Calculation of the diaphragm seal error with the Endress+Hauser Applicator

Diaphragm seal errors are not taken into consideration. They are calculated separately in the Applicator "Sizing Diaphragm Seal".



Reference accuracy [E1]

Reference accuracy comprises the non-linearity [IEC 62828-1 / DIN EN 61298-2] including the hysteresis [IEC 62828-1 / DIN EN 61298-2] and the non-repeatability [IEC 62828-1 / DIN EN 61298-2] in accordance with the limit point method as per [IEC 62828-1 / DIN EN 60770-2]. Reference accuracy for standard up to TD 100:1, for platinum up to TD 5:1.

PMD75

10 mbar (0.15 psi) sensor

- Standard: TD 1:1 = ±0.075 %; TD > 1:1 = ±0.075 % · TD
- Platinum: TD 1:1 = ±0.05 %; TD > 1:1 = ±0.075 % · TD

30 mbar (0.45 psi) sensor

- Standard: $TD \le 3:1 = \pm 0.075$ %; $TD > 3:1 = \pm 0.025$ % · TD
- Platinum: TD 1:1 = ±0.05 %; TD > 1:1 to TD \leq 3:1 = ±0.075 %; TD > 3:1 = ±0.025 % \cdot TD

100 mbar (1.5 psi) sensor

- Standard: $TD \le 5:1 = \pm 0.05$ %; $TD > 5:1 = \pm (0.009 \% \cdot TD + 0.005 \%)$
- Platinum: TD \geq 1:1 = ±0.04 %
- 500 mbar (7.5 psi), 3 bar (45 psi), 16 bar (240 psi), 40 bar (600 psi) sensor
- Standard: $TD \le 15:1 = \pm 0.05$ %; $TD > 15:1 = \pm (0.0015 \% \cdot TD + 0.0275 \%)$
- Platinum: TD \geq 1:1 = ±0.035 %
- 160 bar (2 400 psi) and 250 bar (3 750 psi) gauge pressure sensor and absolute pressure sensor
- Standard: $TD \le 5:1 = \pm 0.10$ %; $TD > 5:1 = \pm 0.02$ % · TD
- Platinum: -

FMD77

100 mbar (1.5 psi) sensor TD $\leq 5:1 = \pm 0.10 \%$; TD > 5:1 = $\pm 0.02 \% \cdot$ TD 500 mbar (7.5 psi) sensor TD $\leq 15:1 = \pm 0.075 \%$; TD > 15:1 = $\pm (0.0015 \% \cdot$ TD + 0.053 %) 3 bar (45 psi) and 16 bar (240 psi) sensor TD $\leq 15:1 = \pm 0.075 \%$; TD > 15:1 = $\pm (0.0015 \% \cdot$ TD + 0.053 %)

FMD77 with capillary on low-pressure side and FMD78

100 mbar (1.5 psi) sensor $TD \le 5:1 = \pm 0.15 \%$; $TD > 5:1 = \pm 0.03 \% \cdot TD$ 500 mbar (7.5 psi) sensor $TD \le 5:1 = \pm 0.15 \%$; $TD > 5:1 = \pm 0.03 \% \cdot TD$ 3 bar (45 psi) and 16 bar (240 psi)sensor

TD $\leq 15:1 = \pm 0.1$ %; TD $> 15:1 = \pm (0.006 \% \cdot \text{TD} + 0.01 \%)$ 40 bar (600 psi) sensor

 $TD \le 15:1 = \pm 0.1 \%$; $TD > 15:1 = \pm (0.006 \% \cdot TD + 0.01 \%)$

Temperature effect [E2]

E2_M - *Main temperature error*

The output changes due to the effect of the ambient temperature [IEC 62828-1 / IEC 61298-3] with respect to the reference temperature [IEC 62828-1 / DIN 16086]. The values specify the maximum error due to min./max. ambient or process temperature conditions.

10 mbar (0.15 psi) and 30 mbar (0.45 psi) sensor

- Standard: ±(0.14 % · TD + 0.04 %)
- Platinum: ±(0.14 % · TD + 0.04 %)

100 mbar (1.5 psi) sensor

- Standard: ±(0.07 % · TD + 0.07 %)
- Platinum: ±(0.07 % · TD + 0.07 %)

500 mbar (7.5 psi) sensor

- Standard: ±(0.03 % · TD + 0.017 %)
- Platinum: ±(0.03 % · TD + 0.017 %)

3 bar (45 psi), 16 bar (240 psi) and 40 bar (600 psi) sensor

- Standard: ±(0.012 % · TD + 0.017 %)
- Platinum: ±(0.012 % · TD + 0.017 %)

160 bar (2 400 psi) gauge pressure sensor and absolute pressure sensor

- Standard: ±(0.042 % · TD + 0.04 %)
- Platinum: •

250 bar (3750 psi) gauge pressure sensor and absolute pressure sensor

- Standard: ±(0.022 % · TD + 0.04 %)
- Platinum: -

E2_E - Electronics error

- Analog output (4 to 20 mA): 0.05 %
- Digital output (HART/PA/FF): 0 %

The additional electronics error that occurs in the temperature range -50 to -41 °C (-58 to -42 °F) is covered by E2LT.

E2_{LT} - low-temperature error

The specifications refer to the calibrated span.

- -40 to +85 °C (-40 to +185 °F): 0 %
- -50 to -41 °C (-58 to -42 °F): 1.5 %

E3_M - Main static pressure error

The static pressure effect refers to the effect on the output due to changes in the static pressure of the process (difference between the output at each static pressure and the output at atmospheric pressure [IEC 62828-2 / IEC 61298-3] and therefore the combination of the influence of the operating pressure on the zero point and the span).

10 mbar (0.15 psi) sensor

- Standard
 - Influence on the zero point: ±0.23 · TD % per 7 bar (105 psi)
 - Influence on the span: ±0.035 % per 7 bar (105 psi)
- Platinum
 - Influence on the zero point: ±0.07 % · TD per 7 bar (105 psi)
 - Influence on the span: ±0.035 % per 7 bar (105 psi)

30 mbar (0.45 psi) sensor

- Standard
 - Influence on the zero point: ±0.70 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.14 % per 70 bar (1050 psi)
- Platinum
 - Influence on the zero point: ±0.25 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.14 % per 70 bar (1050 psi)

100 mbar (1.5 psi) sensor

- Standard
 - Influence on the zero point: ±0.203 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.15 % per 70 bar (1050 psi)
- Platinum
 - Influence on the zero point: ±0.077 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.15 % per 70 bar (1050 psi)

500 mbar (7.5 psi) sensor

- Standard
 - Influence on the zero point: ±0.07 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.10 % per 70 bar (1050 psi)
- Platinum
 - Influence on the zero point: ±0.028 % · TD per 70 bar (1050 psi) • Influence on the span: ± 0.10 % per 70 bar (1050 psi)
- 3 bar (45 psi) sensor
- Standard
 - Influence on the zero point: ±0.049 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.05 % per 70 bar (1050 psi)
- Platinum
 - Influence on the zero point: ±0.021 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.05 % per 70 bar (1050 psi)

16 bar (240 psi) and 40 bar (600 psi) sensor

- Standard
 - Influence on the zero point: ±0.049 % · TD per 70 bar (1050 psi)
 - Influence on the span: ±0.02 % per 70 bar (1050 psi)
- Platinum
 - Influence on the zero point: ±0.021 % · TD per 70 bar (1050 psi) Influence on the span: ±0.02 % per 70 bar (1050 psi)

160 bar (2 400 psi) and 250 bar (3 750 psi) gauge pressure sensor and absolute pressure sensor

- Standard
 - Influence on the zero point: -
 - Influence on the span: -
- Platinum
 - Influence on the zero point: -
 - Influence on the span: -

Resolution Current output: 1 µA

Total error

The total error of the device comprises the total performance and the long-term stability effect and is calculated using the following formula:

Total error = total performance + long-term stability

Calculation of the total error with the Endress+Hauser Applicator

Detailed inaccuracies, e.g. for other temperature ranges, can be calculated with the Applicator "Sizing Pressure Performance".



A003

Calculation of the diaphragm seal error with the Endress+Hauser Applicator

Diaphragm seal errors are not taken into consideration. They are calculated separately in the Applicator "Sizing Diaphragm Seal".



Long-term stability

10 mbar (0.15 psi) and 30 mbar (0.45 psi) sensor

- 1 year: ±0.20 %
- 5 years: ±0.28 %
- 10 years: ±0.31 %
- 100 mbar (1.5 psi) sensor
- 1 year: ±0.08 %
- 5 years: ±0.14 %
- 10 years: ±0.27 %

500 mbar (7.5 psi) sensor

- 1 year: ±0.03 %
- 5 years: ±0.05 %
- 10 years: ±0.08 %

3 bar (45 psi) sensor

- 1 year: ±0.04 %
- 5 years: ±0.08 %
- 10 years: ±0.15 %
- 16 bar (240 psi) sensor
- 1 year: ±0.03 %
- 5 years: ±0.11 %
- 10 years: ±0.21 %

40 bar (600 psi) sensor

- 1 year: ±0.05 %
- 5 years: ±0.07 %
- 10 years: ±0.10 %


160 bar (2 400 psi) and 250 bar (3 750 psi) gauge pressure sensor and absolute pressure sensor

- 1 year: ±0.05 %
- 5 years: ±0.07 %
- 10 years: ±0.10 %

Response time T63 and T90 $\,$

Dead time, time constant

Representation of dead time and time constant as per IEC62828-1:



Dynamic behavior, current output

Туре		Sensor	Dead time (t ₁)	Time constant T63 (t ₂)	Time constant T90 (t ₃)
PMD75 Max.	Max.	 10 mbar (0.15 psi) 30 mbar (0.45 psi) 100 mbar (1.5 psi) 500 mbar (7.5 psi) 3 bar (45 psi) 16 bar (240 psi) 40 bar (600 psi) 	45 ms	 450 ms 450 ms 60 ms 45 ms 40 ms 60 ms 60 ms 	 1040 ms 1040 ms 138 ms 104 ms 92 ms 138 ms 138 ms
		 160 bar (2 400 psi) 250 bar (3 750 psi) 	50 ms	40 ms	90 ms
FMD77, FMD78	Max.	Dependent on the diaphragm se	eal		

Dynamic behavior, digital output (HART electronics)

A typical burst rate of 300 ms results in the following behavior:

Туре		Sensor	Dead time (t ₁)	Dead time (t_1) + Time constant T63 (t_2)	Dead time (t ₁) + Time constant T90 (t ₃)
PMD75 Min	Min.	 10 mbar (0.15 psi) 30 mbar (0.45 psi) 100 mbar (1.5 psi) 500 mbar (7.5 psi) 3 bar (45 psi) 16 bar (240 psi) 40 bar (600 psi) 160 bar (2 400 psi) 250 bar (3 750 psi) 	205 ms	 655 ms 655 ms 265 ms 250 ms 245 ms 265 ms 265 ms 295 ms 295 ms 	 1200 ms 1200 ms 298 ms 264 ms 252 ms 298 ms 298 ms 300 ms 300 ms
	Max.	 10 mbar (0.15 psi) 30 mbar (0.45 psi) 100 mbar (1.5 psi) 500 mbar (7.5 psi) 3 bar (45 psi) 16 bar (240 psi) 40 bar (600 psi) 160 bar (2 400 psi) 250 bar (3 750 psi) 	1005 ms	 1455 ms 1455 ms 1065 ms 1050 ms 1045 ms 1065 ms 1065 ms 1065 ms 1095 ms 1095 ms 	 2000 ms 2000 ms 1098 ms 1064 ms 1052 ms 1098 ms 1098 ms 1100 ms 1100 ms
FMD77, FMD78	Max.	Dependent on the diaphragm se	eal	1	1

Reading cycle

Acyclic: max. 3/s, typically 1/s (depending on command # and number of preambles)
Cyclic (burst): max. 3/s, typically 2/s

The device offers the BURST MODE function for cyclic value transmission via the HART communication protocol.

Cycle time (update time)

Cyclic (burst): min. 300 ms

Dynamic behavior PROFIBUS PA

A typical PLC cycle time of 1 s results in the following behavior:

Туре		Sensor	Dead time (t ₁)	Dead time $(t_1) +$ Time constant T63 (t_2)	Dead time $(t_1) +$ Time constant T90 (t_3)
PMD75 Min	Min.	 10 mbar (0.15 psi) 30 mbar (0.45 psi) 100 mbar (1.5 psi) 500 mbar (7.5 psi) 3 bar (45 psi) 16 bar (240 psi) 40 bar (600 psi) 	80 ms	 530 ms 530 ms 140 ms 125 ms 120 ms 140 ms 140 ms 	 1075 ms 1075 ms 173 ms 139 ms 127 ms 173 ms 173 ms 173 ms
	Max.	 10 mbar (0.15 psi) 30 mbar (0.45 psi) 100 mbar (1.5 psi) 500 mbar (7.5 psi) 3 bar (45 psi) 16 bar (240 psi) 40 bar (600 psi) 	1280 ms	 1730 ms 1730 ms 1340 ms 1325 ms 1320 ms 1340 ms 1340 ms 1340 ms 	 2275 ms 2275 ms 1373 ms 1339 ms 1327 ms 1373 ms 1373 ms 1373 ms
FMD77, FMD78	Max.	Dependent on the diaphragm s	eal	1	1

Read cycle (PLC)

- Acyclic: typically 25/s
- Cyclic: typically 30/s (dependent on the number and type of function blocks used in a closedcontrol loop)

Cycle time (update time)

Min. 200 ms

The cycle time in a bus segment in cyclic data communication depends on the number of devices, on the segment coupler used and on the internal PLC cycle time. A new measured value can be determined up to five times a second.

Dynamic behavior FOUNDATION Fieldbus

A typical configuration for the macro cycle time (host system) of 1 s results in the following behavior:


Туре		Sensor	Dead time (t ₁)	Dead time (t ₁) + Time constant T63 (t ₂)	Dead time (t_1) + Time constant T90 (t_3)
PMD75 Min.	 10 mbar (0.15 psi) 30 mbar (0.45 psi) 100 mbar (1.5 psi) 500 mbar (7.5 psi) 3 bar (45 psi) 16 bar (240 psi) 40 bar (600 psi) 	90 ms	 540 ms 540 ms 150 ms 135 ms 130 ms 150 ms 150 ms 	 1085 ms 1085 ms 183 ms 149 ms 137 ms 183 ms 183 ms 	
	Max.	 10 mbar (0.15 psi) 30 mbar (0.45 psi) 100 mbar (1.5 psi) 500 mbar (7.5 psi) 3 bar (45 psi) 16 bar (240 psi) 40 bar (600 psi) 	1090 ms	 1540 ms 1540 ms 1150 ms 1135 ms 1130 ms 1150 ms 1150 ms 	 2085 ms 2085 ms 1183 ms 1149 ms 1137 ms 1183 ms 1183 ms
FMD77, FMD78	Max.	Dependent on the diaphragm s	eal		

Reading cycle

- Acyclic: typically 10/s
- Cyclic: max. 10/s (dependent on the number and type of function blocks used in a closed-control loop)

Cycle time (update time)

Cyclic: min. 100 ms



Device	Calibration position (A)	Device rotated vertically downwards (B)	Device rotated vertically upwards (C)
PMD75 and silicone oil	No additional error	<+4 mbar (+0.06 psi) The value is doubled for inert oil.	<-4 mbar (-0.06 psi) The value is doubled for inert oil.
FMD77 and silicone oil	No additional error	<+32 mbar (+0.46 psi) The value is doubled for inert oil.	<-32 mbar (-0.46 psi) The value is doubled for inert oil.

Endress+Hauser

Installation factors



A position-dependent zero point shift can be corrected. Please refer to the "Commissioning \rightarrow Position adjustment" section of the Operating Instructions.

Vibration effects

Device/accessory	Measuring cells	Housing	Test standard	Vibration resistance
PMD75	10 mbar (0.15 psi), 30 mbar (0.45 psi)	T14 stainless steel T15 aluminum T17 aluminum	IEC 62828-1 / IEC 61298-3	≤ 0.15% URL to 10 to 38 Hz: ±0.35 mm (0.0138 in); 38 to 2000 Hz: 2 g in all 3 planes
		T14 aluminum	IEC 62828-1 / IEC 61298-3	≤ 0.15% URL to 10 to 60 Hz: ±0.21 mm (0.0083 in); 60 to 2000 Hz: 3 g in all 3 planes
	≥100 mbar (1.5 psi)	T14 stainless steel T15 aluminum	IEC 62828-1 / IEC 61298-3	≤ 0.075 % URL to 10 to 38 Hz: ±0.35 mm (0.0138 in); 38 to 2000 Hz: 2 g in all 3 planes
		T14 aluminum	IEC 62828-1 / IEC 61298-3	≤ 0.075 % URL to 10 to 60 Hz: ±0.35 mm (0.0138 in); 60 to 2000 Hz: 5 g in all 3 planes

Warm-up period


- 4 to 20 mA HART: < 10 s
- PROFIBUS PA: 6 s
- FOUNDATION Fieldbus: 50 s

General installation instructions	 A position-dependent zero point shift can be corrected directly at the device via operating keys, and also in hazardous areas in the case of devices with external operation. Depending on the installation location, diaphragm seals additionally shift the zero point by → 104. The device housing can be rotated up to 380°. Endress+Hauser offers a mounting bracket for installing the device on pipes or walls → 35. Use flushing rings for flange and cell diaphragm seals if buildup or clogging can be expected at the diaphragm seal connection. The flushing ring can be fitted between the process connection and diaphragm seal. Material buildup in front of the process membrane can be flushed away, and the pressure chamber vented, via the two lateral flushing holes. When measuring in media containing solids, such as dirty liquids, installing separators and drain valves is useful for capturing and removing sediment. Using a valve manifold allows for easy commissioning, installation and maintenance without interrupting the process. General recommendations for the piping can be found in the relevant national or international standards. Lay the piping with a monotonic gradient of at least 10 %. When routing the piping outdoors, ensure sufficient anti-freeze protection, e.g. by using pipe heat tracing. Point the cable and plug downwards where possible to prevent moisture from entering (e.g. rain or condensation water).
Measuring arrangement	Flow measurement
	 The PMD75 is best suited to flow measurement. Measuring arrangement for gases: Mount device above the measuring point. Measuring arrangement for liquids and vapors: Mount device below the measuring point. For flow measurement in vapors, mount the condensate traps at the same level as the tapping point and at the same distance from the Deltabar S.
	Level measurement
	The PMD75 and FMD77 are best suited to level measurement in open vessels. All Deltabar S devices are suitable for level measurement in closed vessels.
	 Measuring arrangement for level measurement in open vessels PMD75: Mount device below the lower measuring connection. The negative side is open to atmospheric pressure. FMD77: Mount device directly on the vessel. The negative side is open to atmospheric pressure.
	 Measuring arrangement for level measurement in closed vessels and closed vessels with superimposed vapor PMD75: Mount device below the lower measuring connection. Always connect the negative side above the maximum level via pressure piping. FMD77: Mount device directly on the vessel. Always connect the negative side above the maximum level via pressure piping. In the case of level measurement in closed vessels with superimposed vapor, a condensate trap ensures the pressure remains constant on the negative side.
	Pressure measurement
	 The PMD75 and FMD78 are best suited to differential pressure measurement. Measuring arrangement for gases: Mount device above the measuring point. Measuring arrangement for liquids and vapors: Mount device below the measuring point. For differential pressure measurement in vapors, mount the condensate traps at the same level as the tapping point and at the same distance from the Deltabar S.
Measuring arrangement for devices with diaphragm seals – FMD77 and FMD78	→ 🗎 104
Orientation	The orientation may cause a zero point shift.
	This position-dependent zero point shift can be corrected directly at the device via the operating key, and also in hazardous areas in the case of devices with external operation (position adjustment).

Installation

Wall and pipe mounting, transmitter (optional)

Endress+Hauser offers the following mounting bracket for installing the device on pipes or walls:




- The standard mounting bracket version is **not** suitable for use in an application subject to vibrations.
- The vibration resistance of the heavy-duty mounting bracket has been tested according to IEC 61298-3, see the "Vibration resistance" section $\rightarrow \implies 39$.
- If a valve manifold is used, its dimensions should also be taken into consideration.
- Bracket for wall and pipe mounting including retaining bracket for pipe mounting and two nuts.
- The material of the screws used to secure the device depend on the order code.
- For the technical data (such as the dimensions or order numbers for screws), see the document SD01553P/00/EN.

Ordering information:

- Standard version: Product Configurator, order code for "Additional options" option "Q" or
- Standard version: Product Configurator, order code for "Accessories enclosed" option "PD"
- Heavy-duty version: Product Configurator, order code for "Additional options" option "U" or
- Heavy-duty version: Product Configurator, order code for "Accessories enclosed" option "PB"

Wall and pipe mounting, valve manifold (optional)



For the technical data (such as the dimensions or order numbers for screws), see the document SD01553P/00/EN.

Ordering information:

Product Configurator, order code for "Accessories enclosed", option "PJ"

"Separate housing" version


With the "separate housing" version, you are able to mount the housing with the electronics insert at a distance from the measuring point. This version facilitates trouble-free measurement

- Under particularly difficult measuring conditions (at installation locations that are cramped or difficult to access)
- If rapid cleaning of the measuring point is required and
- If the measuring point is exposed to vibrations.
- You can choose between different cable versions:
- PE: 2 m (6.6 ft), 5 m (16 ft) and 10 m (33 ft)
- FEP: 5 m (16 ft).

Ordering information: Product Configurator, order code for "Additional options 2", version "G".

Dimensions $\rightarrow \square 46$

In the case of the "separate housing" version, the sensor is delivered with the process connection and cable ready mounted. The housing and a mounting bracket are enclosed as separate units. The cable is provided with a socket at both ends. These sockets are simply connected to the housing and the sensor.



Degree of protection for the process connection and sensor with the use of

- FEP cable:
 - IP 69¹⁾
 - IP 66 NEMA 4/6P
 - IP 68 (1.83 mH₂O for 24 h) NEMA 4/6P
- PE cable:
 - IP 66 NEMA 4/6P
 - IP 68 (1.83 mH₂O for 24 h) NEMA 4/6P

Technical data of the PE and FEP cable:

- Minimum bending radius: 120 mm (4.72 in)
- Cable extraction force: max. 450 N (101.16 lbf)
- Resistance to UV light


Use in hazardous area:

- Intrinsically safe installations (Ex ia/IS)
- FM/CSA IS: for Div. 1 installation only

¹⁾ Designation of the IP protection class according to DIN EN 60529. Previous designation "IP69K" according to DIN 40050 Part 9 is no longer valid (standard withdrawn on November 1, 2012). The tests required by both standards are identical.

Reduction of the installation height

If the separate housing is used, the installation height of the process connection is reduced compared to the dimensions of the standard version.




Turning the housing

The housing can be rotated up to 380° by loosening the Allen screw.

Your benefits

- Easy mounting due to optimum alignment of housing
- Good, accessible device operation
- Optimum readability of the onsite display (optional).



Environment


Ambient temperature range

Version	PMD75	FMD77	FMD78
Without LCD display	−50 to +85 ℃ (−5 −54 to +85 ℃ (−6	8 to +185 °F) ¹⁾ 5 to +185 °F) ²⁾	
With LCD display ³⁾	-20 to +70 °C (-4	to +158 °F)	
With separate housing	-	-20 to +60 °C (-4 to +14	40 °F)
Diaphragm seal systems ⁴⁾	-	→ 🖺 106	

- 1) If the temperature is below -40 °C (-40 °F), the chance of failure increases. Product Configurator, order code for "Test, Certificate" option "JN".
- If the temperature is below -40 °C (-40 °F), the chance of failure increases. Product Configurator, order code for "Test, Certificate" option "JT".
- 3) Extended temperature application range (-50 to +85 °C (-58 to +185 °F)) with restrictions in optical properties, such as display speed and contrast
- 4) Ambient temperature range and process temperature range are mutually dependent see "Heat insulation" section $\rightarrow \cong 106$

PMD75: Ambient temperature T_a depending on the process temperature T_p

The process connection must be fully insulated for ambient temperatures below -40 °C (-40 °F).



1 Insulation material

Hazardous area

- For devices for use in hazardous areas, see Safety Instructions, Installation or Control Drawing $\rightarrow \cong 119$.
- Pressure measuring devices that have the usual explosion protection certificates (e.g. ATEX-/ CSA-/ FM-/ IEC Ex,...) can be used in hazardous areas at ambient temperatures down to -50 °C (-58 °F) (order code for "Test, Certificate" option "JN"). The functionality of the explosion protection is also guaranteed for ambient temperatures down to -50 °C (-58 °F).
- Pressure measuring devices that have the usual explosion protection certificates (e.g. ATEX-/ IEC Ex, etc.) can be used in hazardous areas at ambient temperatures down to -54 to +85 °C (-65 to +185 °F)(order code for "Test, Certificate" option "JT"). The functionality of the explosion protection is also guaranteed for ambient temperatures down to -50 °C (-58 °F). At temperatures ≤ -50 °C (-58 °F), explosion protection is guaranteed by the housing in the case of flameproof enclosure (Ex d) type of protection. The functionality of the transmitter cannot be fully guaranteed.

Storage temperature range	 -40 to +90 °C (-40 to +194 °F) Option -50 to +90 °C (-58 to +194 °F) order code 580 "Test, Certificate" option "JN". If the temperature is below -40 °C (-40 °F), the probability of a failure increases. Option -54 to +90 °C (-65 to +194 °F) order code 580 "Test, Certificate" option "JT". If the temperature is below -40 °C (-40 °F), the probability of a failure increases. Local display: -40 to +85 °C (-40 to +185 °F) Separate housing:-40 to +60 °C (-40 to +140 °F) Devices with PVC-armored capillary: -25 to +80 °C (-13 to +176 °F)
Degree of protection	Depends on the deployed housing: →
Climate class	Class 4K4H (air temperature: –20 to +55 °C (–4 to +131 °F), relative humidity: 4 to 100%) satisfied as per DIN EN 60721-3-4 (condensation possible)
Electromagnetic compatibility	 Electromagnetic compatibility as per EN 61326 and NAMUR recommendation EMC (NE21). With enhanced immunity against electromagnetic fields as per EN 61000-4-3: 30 V/m with closed cover (for devices with T14 housing or T15 housing) Maximum deviation: < 0.5 % of span All EMC measurements were performed with a turn down (TD) = 2:1. For further details refer to the Declaration of Conformity.

Vibration resistance

Device/accessory	Measuring cells	Housing	Test standard	Vibration resistance
PMD75	10 mbar (0.15 psi),	T14 stainless steel T15 aluminum T17 aluminum	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 38 Hz: ±0.35 mm (0.0138 in); 38 to 2000 Hz: 2 g in all 3 axes
	30 mbar (0.45 psi)	T14 aluminum	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 60 Hz: ±0.21 mm (0.0083 in); 60 to 2000 Hz: 3 g in all 3 axes
PMD75	≥ 100 mbar (1.5 psi)	T14 stainless steel T15 aluminum	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 38 Hz: ±0.35 mm (0.0138 in); 38 to 2000 Hz: 2 g in all 3 axes
FMD78 transmitter		T14 aluminum	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 60 Hz: ±0.35 mm (0.0138 in); 60 to 2000 Hz: 5 g in all 3 axes
PMD75 and FMD78 transmitters with mounting bracket (heavy duty design)	All	All	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 60 Hz: ±0.15 mm (0.0059 in); 60 to 500 Hz: 2 g in all 3 axes
FMD77	All	All	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 60 Hz: ±0.075 mm (0.0030 in); 60 to 150 Hz: 1 g in all 3 axes
Process connection with capillary	All	All	IEC 62828-1 / IEC 61298-3	Guaranteed for 10 to 60 Hz: ±0.35 mm (0.0138 in); 60 to 1000 Hz: 5 g in all 3 axes

Oxygen applications

Oxygen and other gases can react explosively to oils, grease and plastics, such that, among other things, the following precautions must be taken:

- All components of the system, such as measuring devices, must be cleaned in accordance with the BAM requirements.
- Depending on the materials used, a certain maximum temperature and a maximum pressure must not be exceeded for oxygen applications.

The devices suitable for gaseous oxygen applications are listed in the following table with the specification $\ensuremath{p_{\text{max}}}$

Order code for devices ¹⁾ , cleaned for oxygen applications	p _{max} for oxygen applications	T _{max} for oxygen applications
PMD75 - * * * * * * * * K * * or PMD75 - * * * * * * * H * * HB	80 bar (1200 psi)	60 °C (140 °F)
PMD75 - * * * * * * * 2 * * or PMD75 - * * * * * * * A * * HB	80 bar (1200 psi)	60 °C (140 °F)
PMD75 - * * * * * * * 3 * * or PMD75 - * * * * * * * C * * HB	80 bar (1200 psi)	60 °C (140 °F)
FMD77 - * * * * * T * F * * or FMD77 - * * * * * D * F * * HB	PN of the flange, max. 80 bar (1200 psi)	60 °C (140 °F)
FMD78 - * * * * * * 4 * * or FMD78 - * * * * * * 6 * * HB FMD78 - * * * * * * D * * or FMD78 - * * * * * F * * HB	PN of the flange, max. 80 bar (1200 psi)	60 °C (140 °F)

HB = Cleaned for oxygen service

1) Devices only, not accessories or enclosed accessories.

Ultrapure gas applications	Endress+Hauser also offers devices for special applications, such as ultrapure gas, cleaned from oil and grease. No special restrictions regarding the process conditions apply to these devices.		
	 Ordering information: PMD75: Product Configurator, order code for "Seal" FMD77: Product Configurator, order code for "Process connection low-pressure side; Material; Seal". 		
Hydrogen applications	A gold-coated metal process isolating diaphragm offers universal protection against hydrogen diffusion, both in gas applications and in applications with aqueous solutions.		
	Applications with hydrogen in aqueous solutions		
	A gold/rhodium-coated metal process isolating diaphragm (AU/Rh) offers effective protection against hydrogen diffusion.		
Operation in very corrosive environment	PMD75: For corrosive environments (e.g. maritime environment / coastal areas), Endress+Hauser recommends the protective terminal for maritime environments (available as mounted accessory).		
	Diaphragm seal FMD78 and FMD77 with capillary on low-pressure side:		
	For corrosive environments (e.g. maritime environment / coastal areas), Endress+Hauser recommends the use of a PVC or PTFE armor for the capillaries ($\rightarrow \square 89$). The transmitter can also be protected by a special coating (T echnical S pecial P roduct (TSP)).		

Process

Process temperature limits (temperature at transmitter)


PMD75

- Process connections made of 316L or Alloy C276:
 - −50 to +85 °C (−58 to +185 °F)
- Process connections made of C22.8: -10 to +85 °C (+14 to +185 °F)
- For oxygen applications, see the $\rightarrow \cong$ 40"Oxygen applications" section.
- Pay attention to the process temperature range of the seal. See also the following section "Process temperature range, seals".

PMD75 with valve manifold

The maximum permitted process temperature at the manifold is 110 °C (230 °F).

For process temperatures >85 $^{\circ}$ C (185 $^{\circ}$ F)C where non-insulated side flanges are installed horizontally on a valve manifold, a reduced ambient temperature applies (see the following graphic).



T_a Maximum ambient temperature at the manifold

T_p Maximum process temperature at the manifold

FMD77

- Depends on the design (see the following table)
- Dependent on diaphragm seal and filling oil (→ 🗎 103): -70 to +400 °C (-94 to +752 °F)
- For oxygen applications, see the $\rightarrow \ \binomega$ 40"Oxygen applications" section.
- Pay attention to the process temperature range of the seal. See also the following section "Process temperature range, seals".
- Please observe the temperature application limits of the diaphragm seal oil. →
 ⁽¹⁾ 103, "Diaphragm seal filling oils" section.
- Please observe the maximum gauge pressure and maximum temperature.

i

Design	Temperature isolator	Temperature	Option ¹⁾
Transmitter horizontal	long	400 °C (752 °F)	MA
Transmitter vertical	long	300 °C (572 °F)	MR
Transmitter horizontal	short	200 °C (392 °F)	MC

Design	Temperature isolator	Temperature	Option ¹⁾
Transmitter vertical	short	200 °C (392 °F)	MD
U-bracket, Transmitter horizontal (for devices which require a CRN approval)	-	400 °C (752 °F)	2)

1) Product Configurator, order code for "Process connection"

2) In combination with CSA approval.

FMD78

- Dependent on diaphragm seal and filling oil:-70 to +400 °C (-94 to +752 °F)
- For oxygen applications, see the $\rightarrow \cong 40^{\circ}$ Oxygen applications" section.
- Please observe the temperature application limits of the diaphragm seal oil. →
 ⁽¹⁾ 103, "Diaphragm seal filling oils" section.
- Please observe the maximum gauge pressure and maximum temperature.

FMD77 and FMD78: Devices with PTFE-coated process isolating diaphragm

The non-stick coating has excellent gliding properties and is used to protect the process isolating diaphragm against abrasive media.

NOTICE


й

Incorrect use of the PTFE foil will destroy the device!


• The PTFE foil is designed to protect the unit against abrasion. It does not provide protection against corrosive media.

Range of application of the PTFE foil

For the range of application of the 0.25 mm (0.01 in) PTFE foil on an AISI 316L (1.4404/1.4435) process isolating diaphragm, see the following diagram:



For vacuum applications: $p_{abs} \le 1$ bar (14.5 psi)to 0.05 bar (0.725 psi)up to max. +150 °C (302 °F).



A002809

Process temperature range, seals

PMD75

Seal	Process temperature range	Option ¹⁾
FKM	-20 to +110 °C (-4 to +230 °F) ²⁾	A
PTFE	-40 to +110 °C (-40 to +230 °F) ^{2) 3)}	С
NBR	–20 to +85 °C (–4 to +185 °F)	F
Copper	-40 to +85 °C (-40 to +185 °F)	Н
Copper, cleaned for oxygen service	-20 to +60 °C (-4 to +140 °F)	K or H ⁴⁾
FKM, cleaned from oil+grease	-20 to +110 °C (-4 to +230 °F)	1
FKM, cleaned for oxygen service	-20 to +60 °C (-4 to +140 °F)	2 or A ⁴⁾
PTFE, cleaned for oxygen applications	-20 to +60 °C (-4 to +140 °F)	3 or C ⁴⁾
EPDM ⁵⁾	-40 to +85 °C (-40 to +185 °F)	J

1) Product Configurator, order code for "Seal"

2) For process temperatures > 85 °C (185 °F) pay attention to the ambient temperature and installation → 🛱 41

3) For pressures > 160 bar (2 320 psi) process temperature is limited to -20 °C (-4 °F)

with option "HB", see Product Configurator, order code for "Service" 4)

Always for LP side with blind flange (see Product Configurator, order code for "Process connection"). 5)

FMD77 (with diaphragm seal)

Seal on the LP side (-)	Process temperature range ¹⁾	OPL bar (psi)	PN bar (psi)	Option ²⁾
FKM	-20 to +85 °C (-4 to +185 °F)	See the "Measuring range" section	See the "Measuring range" section "FMD77, FMD78, PMD75: Option PN 160 / 16 MPa / 2400 psi" → 🗎 12.	
PTFE	-40 to +85 °C (-40 to +185 °F)	· · · ·		
EPDM	-40 to +85 °C (-40 to +185 °F)			
FKM, cleaned from oil +grease	–10 to +85 °C (+14 to +185 °F)			S
FKM, cleaned for oxygen service ³⁾	-10 to +60 °C (+14 to +140 °F)			T or D ⁴⁾
Kalrez, Compound 6375	0 to +5 °C (+32 to +41 °F)	44 to 49 (660 to 735)	29 to 33 (435 to 495)	M, N
	+5 to +10 °C (+41 to +50 °F)	49 to 160 (735 to 2400)	33 to 107 (495 to 1605)	
	+10 to +85 °C (+50 to +185 °F)	160 (2400)	107 (1605)	
Chemraz, Compound 505	-10 to +25 °C (+14 to +77 °F)	130 to 160 (1950 to 2400)	87 to 107 (1305 to 1605)	P, Q
	+25 to +85 °C (+77 to +185 °F)	160 (2400)	107 (1605)	
Diaphragm seal and capillary, welded	Please observe the temperature ap	pplication limits of the diaphragm seal	oil. → 🗎 103, "Diaphragm seal f	illing oils" section.

1) Lower temperatures on request

Product Configurator, order code for "Process connection, LP side; seal:" 2)

3) 4)

Observe "Oxygen applications" section With option "HB", see Product Configurator, order code for "Service"

essure specifications	WARNING				
	The maximum pressure for the measuring device depends on the lowest-rated element with				
	regard to pressure.				
	► For pressure specifications, see the "Measuring range" section and the "Mechanical construction"				
	section. The measuring d	levice must be operated only v	within the specified limits!		
	 Maximum worki value is based or an unlimited per pressure. For the standards EN 10 and 1.4404 are q materials can be in each case). The overpressure x maximum work any lasting dama The Pressure Equ corresponds to th For sensor range process connecti the very maximu sensor range, sel pressure = PN) In oxygen applicate exceeded → ● 4 The sensors were changes up to a for the 10 mbar 0 to 100 bar (0 to 100 bar (0	ing pressure: The maximum with a reference temperature of 4- tiod of time. Observe the temperature of 4- tiod of time. Observe the temperature of 4- tiod of time. Observe the temperature of 4- identical of the star grouped together under EN 10- identical.), ASME B 16.5a, JK e limit corresponds to the over king pressure) and may be ap age. uipment Directive (2014/68/ he maximum working pressure and process connection comion is less than the nominal va- im, to the OPL value of the pre- lect a process connection with ations, the values for "p _{max} an 40. e designed for high pressure for nominal pressure of 0 to 420 (0.15 psi) and 30 mbar (0.45 to 1450 psi), use FKM, EPDM the maximum working pressure of the maximum working pressure of 0 to 420 the maximum working pressure of 0 to 450 psi), use FKM, EPDM	vorking pressure is specified on the nameplate. Thi $120 ^{\circ}C (+68 ^{\circ}F)$ and may be applied to the device for berature dependency of the maximum working thigher temperatures for flanges, please refer to ability-temperature property, the materials 1.4435 092-1; the chemical composition of the two S B 2220 (the latest version of the standard applies rpressure limit of the individual sensors (OPL = 1.5 oplied only for a limited period of time to prevent EU) uses the abbreviation "PS". The abbreviation "PS the of the measuring device. binations where the overpressure limit (OPL) of the alue of the sensor, the device is set at the factory, a ocess connection. If you want to use the entire a higher OPL value (1.5 x PN; maximum working d T _{max} for oxygen applications must not be ratings with load change. For very frequent load bar (0 to 6 092 psi), check the zero point regularly 5 psi) sensors, with regular load changes >		
	Burst pressure				
	Device	Measuring range	Burst pressure 1)		
	PMD75 PN160	≤40 bar (580 psi)	690 bar (10005 psi) ²⁾		
			600 bar (8700 psi) ³⁾		
			1600 bar (23 200 psi) ^{2) 4) 5)} .		

- Excluding FMD77 and FMD78 with mounted diaphragm seal system Applies to the process seal materials FKM, PTFE, NBR, EPDM and to pressure applied on both sides. 1) 2) 3) 4) 5)

Applies to the process seal material PTFE and to side vent. If the side vent valves (sv) option is selected, the burst pressure is 690 bar (10005 psi)

. The burst pressure for the process seal material PTFE (PN250) is 1250 bar (18125 psi)

Mechanical construction

F Fo

For the dimensions, see the Product Configurator: www.endress.com

Search for product \rightarrow click "Configuration" to the right of the product image \rightarrow after configuration click "CAD"

The following dimensions are rounded values. For this reason, they may deviate slightly from the dimensions given on www.endress.com.

Device height

The device height is calculated from

- the height of the housing
- the height of optional mounted parts such as temperature isolators or capillaries
- the height of the relevant process connection.

The individual heights of the components can be found in the following sections. To calculate the device height, simply add up the individual heights of the components. If necessary, the installation space (the space used to install the device) must also be taken into account. You can use the following table for this:

Designation	Item	Dimension	Example with PMD75
Side flanges	(A)	85 mm (3.35 in)	
Height of housing	(B)	→ 🖺 47 ff.	HE CONTRACTOR
Installation space	(C)	-	
			A0023927
Device height			

Designation	Item	Dimension	Example with FMD77
Mounted parts	(A)	→ 🖺 54	
Side flanges	(B)	85 mm (3.35 in)	
Height of housing	(C)	→ 🖺 47 ff.	
Installation space	(D)	-	
Process connections	(b)	→ 🖺 49	
Device height			

Designation	Item	Dimension	Example with FMD78
Side flanges	(A)	85 mm (3.35 in)	C
Height of housing	(B)	→ 🗎 47 ff.	
Installation space	(C)	-	
			A0025881
Process connections	(b)	→ 🖺 49	
Device height			


T14 housing, optional display on the side Image: transformation of transformation of the side Image: transformation of transformation o

Material		Degree of protection	Cable entry			Option ¹⁾
Housing	Cover seal	_		with display	without display	
		IP66/67 NEMA 6P	M20 gland			А
		IP66/67 NEMA 6P	G ½" thread			A B C D E F G H 1 2 3 4 5
		IP66/67 NEMA 6P	NPT ½" thread			
A 1	EPDM	IP66/67 NEMA 6P	M12 plug	1.2 (2.65)	· · · · · · · · · · · · · · · · · · ·	D
Aluminum		IP66/67 NEMA 6P	7/8" plug	1.2 (2.65)	1.1 (2.43)	E
		IP65 NEMA 4	HAN7D plug 90 degrees			F
	FVMQ	IP66/67 NEMA 6P	M20 gland			G
	FVMQ	IP66/67 NEMA 6P	NPT ½" thread			Н
		IP66/67 NEMA 6P	M20 gland			1
		IP66/67 NEMA 6P	G ½" thread			2
	EPDM	IP66/67 NEMA 6P	NPT ½" thread			3
316L	EPDIM	IP66/67 NEMA 6P	M12 plug	2.1.(4.62)	2.0 (4.41)	4
316L		IP66/67 NEMA 6P	7/8" plug	2.1 (4.63)	2.0 (4.41)	5
		IP65 NEMA 4	HAN7D plug 90 degrees			6
	FVMQ	IP66/67 NEMA 6P	M20 gland			7
	FVMQ	IP66/67 NEMA 6P	NPT ½" thread			8

1) Product Configurator, order code for "Housing, cover seal, cable entry, degree of protection"

A0019997


T15 housing, optional display on the top



Material		Degree of protection	Cable entry	Weight in kg (lb)	Option ¹⁾
Housing	Cover seal			with display	without display	
		IP66/67 NEMA 6P	M20 gland			J
		IP66/67 NEMA 6P	G ½" thread		К	К
A 1	EPDM	IP66/67 NEMA 6P	NPT ½" thread		1 7 (2 75)	L
Aluminum	EPDIM	IP66/67 NEMA 6P	M12 plug	1.8 (3.97)	1.7 (3.75)	М
		IP66/67 NEMA 6P	7/8" plug			N
		IP65 NEMA 4	HAN7D plug 90 degrees	1		Р

1) Product Configurator, order code for "Housing, cover seal, cable entry, degree of protection"

T17 housing (hygienic), optional display on the side




Material		Degree of protection ¹⁾	Cable entry	Weight in kg (lb)		Option ²⁾
Housing	Cover seal			with display	without display	
	IP66/68 NEMA 6P	IP66/68 NEMA 6P	M20 gland			R
		IP66/68 NEMA 6P	G ½" thread			S
316L	EPDM	IP66/68 NEMA 6P	NPT ½" thread	1.2 (2.65)	1.1 (2.43)	Т
		IP66/68 NEMA 6P	M12 plug			U
		IP66/68 NEMA 6P	7/8" plug			V

1) Degree of protection IP 68: 1.83 mH_2O for 24 h

2) Product Configurator, order code for "Housing, cover seal, cable entry, degree of protection"

Process connections PMD75 Oval flange, connection 1/4-18 NPT or RC 1/4



Connection	Mounting	Material	Accessories	Weight 1)	Option ²⁾
				kg (lbs)	
1/4-18 NPT IEC 61518	7/16-20 UNF	Steel C 22.8 (1.0460/Zn5) ³⁾	incl. 2 vent valves	4.2 (9.26)	В
1/4-18 NPT IEC 61518	7/16-20 UNF	1.4408 / CF3M ⁴⁾ / AISI 316L	AISI 316L (1.4404)		D ⁵⁾
		AISI 316L (1.4404) ⁶⁾			
1/4-18 NPT IEC 61518	7/16-20 UNF	Alloy C276 (2.4819)	Vent valves Alloy C276 (2.4819) ⁷⁾	4.5 (9.92)	F ⁵⁾
RC 1/4	7/16-20 UNF	1.4408 / CF3M ⁴⁾ / AISI 316L	incl. 2 vent valves	4.2 (9.26)	U
		AISI 316L (1.4404) ⁶⁾	AISI 316L (1.4404)		
1/4-18 NPT IEC 61518	PN 160: M10PN 420: M12	Steel C 22.8 (1.0460/Zn5) ³⁾			1
1/4-18 NPT IEC 61518	PN 160: M10PN 420: M12	AISI 316L (1.4404)			2
1/4-18 NPT IEC 61518	 PN 160: M10 PN 420: M12 	Alloy C276 (2.4819)	Vent valves Alloy C276 (2.4819) ⁷⁾	4.5 (9.92)	3
HP: 1/4-18 NPT IEC 61518 LP: blind flange	7/16-20 UNF	AISI 316L (1.4404)	incl. vent valve AISI 316L (1.4404)	4.2 (9.26)	Q ⁵⁾
HP: 1/4-18 NPT IEC 61518 LP: blind flange	7/16-20 UNF	Alloy C276 (2.4819)	without vent valve ⁷⁾ .	4.5 (9.92)	S ⁵⁾

Weight of process connections without vent valves with 10 mbar (0.15 psi)or 30 mbar (0.45 psi)measuring cell, process connections without vent valves with measuring cells ≥ 100 mbar (1.5 psi) weigh approx. 800 g (28.22 oz) less.

2) Product Configurator, order code for "Process connection"

3) The C22.8 side flanges are coated with anti-corrosion protection (zinc, chrome). To prevent the formation of hydrogen and thereby diffusion through the membrane, Endress+Hauser recommends the use of 316L side flanges for applications involving water. Hydrogen diffusion through the diaphragm leads to measurement errors, or in extreme cases to a device failure.

4) Cast equivalent to material AISI 316L


5) These process connections are CRN-approved. If the CRN approval option is ordered, the MWP for the variants without side vent is limited to a MWP of 262 bar (3 800 psi) (at 120 °C (248 °F))

6) For devices with CSA approval: Product Configurator, order code for "Approval", options D, E, F, U, V, W and X

7) Product Configurator, order code for "Additional options 2"

Process connections PMD75

Oval flange, connection 1/4-18 NPT or RC 1/4, with side vent



Connection	Mounting	Material	Accessories	Weight 1)	Option ²⁾
				kg (lbs)	
1/4-18 NPT IEC 61518	7/16-20 UNF	Steel C 22.8 (1.0460/Zn5) ³⁾	4 locking screws and	4.2 (9.26)	С
1/4-18 NPT IEC 61518	7/16-20 UNF	1.4408 / CF3M ⁴⁾ / AISI 316L	2 vent valves AISI 316L (1.4404)		E ⁵⁾
		AISI 316L (1.4404) 6)			
1/4-18 NPT IEC 61518	7/16-20 UNF	Alloy C276 (2.4819)	Vent valves Alloy C276 (2.4819) 7)	4.5 (9.92)	H ⁵⁾
RC 1/4	7/16-20 UNF	1.4408 / CF3M ⁴⁾ / AISI 316L	4 locking screws and	4.2 (9.26)	V
		AISI 316L (1.4404) ⁶⁾	2 vent valves AISI 316L (1.4404)		
HP: 1/4-18 NPT IEC 61518 LP: blind flange	7/16-20 UNF	AISI 316L (1.4404)	incl. locking screws and vent valve AISI 316L (1.4404)	4.2 (9.26)	R ⁵⁾
HP: 1/4-18 NPT IEC 61518 LP: blind flange	7/16-20 UNF	Alloy C276 (2.4819)	Vent valve Alloy C276 (2.4819) ⁷⁾	4.5 (9.92)	T ⁵⁾

1) Weight of process connections without vent valves with 10 mbar (0.15 psi) or 30 mbar (0.45 psi) measuring cell, process connections without vent valves with measuring cells \geq 100 mbar (1.5 psi) weigh approx. 800 g (28.22 oz) less.

2) Product Configurator, order code for "Process connection"

3) The C22.8 side flanges are coated with anti-corrosion protection (zinc, chrome). To prevent the formation of hydrogen and thereby diffusion through the membrane, Endress+Hauser recommends the use of 316L side flanges for applications involving water. Hydrogen diffusion through the diaphragm leads to measurement errors, or in extreme cases to a device failure.


4) Cast equivalent to material AISI 316L

5) These process connections are CRN-approved. If the CRN approval option is ordered, the MWP for the variants with side vent is limited to a MWP of 179 bar (2 600 psi) (at 120 °C (248 °F))

6) For devices with a CSA approval: Product Configurator, order code for "Approval", options D, E, F, U, V, W and X

7) Product Configurator, order code for "Additional options 2"

Process connections PMD75 Oval flange, prepared for diaphragm seal mount




Material	Option ¹⁾
1.4408 / CF3M ²⁾ / AISI 316L	W
AISI 316L (1.4404) ³⁾	

- 1) Product Configurator, order code for "Process connection"
- 2) Cast equivalent to material AISI 316L
- 3) For devices with CSA approval: Product Configurator, order code for "Approval", options D, E, F, U, V, W and X

Valve manifold DA63M-(optional)

Endress+Hauser supplies milled valve manifolds via the transmitter's product structure in the following versions:



3-way or 5-way valve manifolds in 316L or AlloyC can be


- ordered as an **enclosed** accessory (screws and seals for mounting are enclosed)
- ordered as a mounted accessory (mounted valve manifolds are supplied with a documented leakage test).

Certificates ordered with the equipment (e.g. 3.1 material certificate and NACE) and tests (e.g. PMI and pressure test) apply to the transmitter and the valve manifold.

For other details (order option, dimension, weight, materials), see SD01553P/00/EN "Mechanical accessories for pressure measuring devices".

During the operating life of the valves, it may be necessary to re-tighten the packing.


Mounting on valve manifold




Item	Designation	Option ¹⁾
А	Mounting from above on valve manifold	NV
В	Mounting from below on valve manifold	NW


1) Product Configurator, order code for "Accessories mounted"

FMD77: Selecting the process connection and capillary line	The device can be fitted with different process connections on the high-pressure side (HP) and on the low-pressure side (LP).
	The FMD77 can also be fitted with capillary lines on the low-pressure side (LP).
	When using diaphragm seal systems with a capillary, sufficient strain relief must be provided to prevent the capillary from bending (capillary bending radius ≥ 100 mm (3.94 in)).
	 Example: Process connection on high-pressure side = DN80 flange Process connection on low-pressure side = DN50 flange
	 Your benefits: Thanks to the variety of order options, the devices can be optimally adapted to the given installation situation Reduced costs due to optimum system design Easier installation due to adjusted length of capillary line Easier adaptation to existing installation situations
	 Ordering information: Process connections are indicated in the relevant section by HP (high-pressure side) and LP (low-pressure side) Order details for capillary lengths → 91




Due to the use of different process connections and capillary lines, it is essential that the device be designed/ordered using the "Applicator Sizing Diaphragm Seal" selection tool, which is available free of charge. Additional information can be found in the "Planning instructions, diaphragm seal systems" section → 🖺 100





Item	Design	Temperature isolator	Page	Option ¹⁾
А	Transmitter horizontal	long	→ 🗎 55	MA ²⁾
В	Transmitter vertical	long	→ 🗎 55	MB
С	Transmitter horizontal	short	→ 🗎 55	MC
D	Transmitter vertical	short	→ 🗎 55	MD


1) 2) Product Configurator, order code for "Design; temperature isolator" Standard




Item	Design	Page	Option ¹⁾
E	U-bracket, Transmitter horizontal (for devices which require a CRN approval)	→ 🖺 56	In combination with CSA approval.

1) Product Configurator, order code for "Process connection" Process connections FMD77 with diaphragm seal, highpressure side

Device with long temperature isolator




Device with short temperature isolator



Process connections FMD77 with diaphragm seal, highpressure side

U-bracket with CRN approval




Process connections FMD77 with diaphragm seal

• The following drawings are schematic diagrams. In other words, the dimensions of a

diaphragm seal supplied may deviate from the dimensions specified in this document.

- Observe the information in the "Planning instructions for diaphragm seal systems" section $\rightarrow \ \boxdot \ 100$
- For further information please contact your local Endress+Hauser Sales Center.

EN flanges, connection dimensions in accordance with EN 1092-1



Flange ^{1) 2) 3)}					Boltholes	Boltholes			Option		
4)	Nominal pressure	Туре	D	b	g	Number	g ₂	k	Weight		
	PN		[mm]	[mm]	[mm]	_	[mm]	[mm]	[kg (lb)]	HP ⁵⁾	LP ⁶⁾
DN 50	10-40	B1	165	20	102	4	18	125	3.0 (6.62)	A ⁷⁾⁸⁾	TA ^{7) 8)}
DN 80	10-40	B1	200	24	138	8	18	160	5.2 (11.47)	B ^{7) 8)}	TB ^{7) 8)}
DN 100	10-16	B1	220	20	-	8	18	180	4.8 (10.58)	F	TC
DN 100	25-40	B1	235	24	162	8	22	190	6.7 (14.77)	G	TD

1) Material: AISI 316L

2) The roughness of the surface in contact with the medium including the raised face of the flanges (all standards) made of Alloy C276, Monel, tantalum, gold > 316L or PTFE is $R_a < 0.8 \ \mu m$ (31.5 μin). Reduced surface roughness available on request.

3) The raised face of the flange is made of the same material as the process membrane.

4) Nominal diameter

5) Product Configurator, order code for "Process connection, HP/ HP+LP:"


6) Product Configurator, order code for "Alternative process connection LP side:"

7) Alternatively available with TempC membrane.

8) Alternatively available with gold-coated TempC membrane (Product Configurator, order code for "Membrane material" option "G/D").

DN	PN			Ød _M (r	nm)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
DN 50	PN 10-40	61	58	57	60	59	52
DN 80	PN 10-40	89	89	89	92	89	80
DN 100	PN 10-16	-	80	90	92	89	-
DN 100	PN 25-40	-	80	90	92	89	-

Maximum diameter of membrane $\mathcal{O}d_M$



EN flanges with barrel (extended diaphragm seal), connection dimensions in accordance with EN 1092-1

Flange	1) 2)							Boltholes			Diaphragm seal		Option ³⁾
4)	Nominal pressure	Туре	D	b	g	L	d ₃	Number	g ₂	k	d _M	Weight	(HP + LP)
	PN		[mm]	[mm]	[mm]	[mm]	[mm]		[mm]	[mm]	[mm]	[kg (lb)]	
DN 80	10-40	B1	200	24	138	50	76	8	18	160	72	6.2 (13.67)	С
						100						6.7 (14.77)	
						200						7.8 (17.20)	

1) Material: AISI 316L


2) In the case of process membranes made of Alloy C276, Monel oder tantalum, the raised face of the flange and the barrel pipe are made of 316L.

3) Product Configurator, order code for "Process connection, HP/ HP+LP:"

4) Nominal diameter

Process connections FMD77 with diaphragm seal

ASME flanges, connection dimensions in accordance with B 16.5, raised face RF



Flange ^{1) 2) 3)}					Boltholes			Diaphragm seal	4) 5)	Option	
Nominal diameter	Class	D	b	g	Number	g ₂	k	Weight			
[in]	[lb./sq.in]	[in]	[in]	[in]	_	[in]	[in]	[kg (lb)]		HP ⁶⁾	LP ⁷⁾
2	150	6	0.75	3.62	4	0.75	4.75	2.6 (5.73)	CRN	N ^{8) 9)}	TE ^{8) 9)}
2	300	6.5	0.88	3.62	8	0.75	5	3.4 (7.5)	CRN	O ⁸⁾⁹⁾	TF ^{8) 9)}
2	400/600	6.5	1	3.62	8	0.75	5	4.3 (9.48)	-	J	-
3	150	7.5	0.94	5	4	0.75	6	5.1 (11.25)	CRN	P ^{8) 9)}	TG ^{8) 9)}
3	300	8.25	1.12	5	8	0.75	6	7.0 (15.44)	CRN	R ^{8) 9)}	TH ^{8) 9)}
4	150	9	0.94	6.19	8	0.75	7.5	7.2 (15.88)	CRN	Т	TI
4	300	10	1.25	6.19	8	0.88	7.88	11.7 (25.8)	CRN	W	TJ

Material: AISI 316/316L. Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual-rated)
 The roughness of the surface in contact with the medium, including the raised face of the flanges (all standards) made of Alloy C276, Monel,

tantalum, gold or PTFE, is R_a < 0.8 μ m (31.5 μ in). Reduced surface roughness available on request.

3) The raised face of the flange is made of the same material as the process membrane.

4) Approval

5) CSA approval: Product Configurator, order code for "Approval"

6) Product Configurator, order code for "Process connection, HP/ HP+LP:"


7) Product Configurator, order code for "Alternative process connection LP side:"

8) Alternatively available with TempC membrane.

9) Alternatively available with gold-coated TempC membrane (Product Configurator, order code for "Membrane material" option "G/D").

NPS	Class			Ød _M (in)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)
2	150	2.40	-	2.44	2.44	2.44
2	300	2.40	-	2.44	2.44	2.44
2	400/600	-	2.05	2.44	2.44	2.44
3	150	3.50	-	3.62	3.62	3.62
3	300	3.50	-	3.62	3.62	3.62
4	150	-	3.15	3.62	3.62	3.62
4	300	-	3.15	3.62	3.62	3.62

Maximum diameter of membrane $Ød_M$



ASME flanges with barrel (extended diaphragm seal), connection dimensions in accordance with ASME B 16.5, raised face RF

Flange ^{1) 2)}							Boltholes			3)	Weight	Option ⁴⁾
Nominal diameter	Class	D	b	g	L	d ₃	Number g ₂ k		d _M		(HP + LP)	
[in]	[lb./sq.in]	[in]	[in]	[in]	[in]	[in]		[in]	[in]		[kg (lb)]	
3	150	7.5	0.94	5	2	2.99	4	0.75	6	2.83	6 (13.23)	Q
					4]					6.6 (14.55)	
					6]					7.1 (15.66)	
					8]					7.7 (16.98)]

1) Material: AISI 316/316L


2) In the case of process membranes made of Alloy C276, Monel oder tantalum, the raised face of the flange and the barrel pipe are made of 316L.

3) Diaphragm seal

4) Product Configurator, order code for "Process connection, HP/ HP+LP:"

Process connections FMD77 with diaphragm seal

JIS flanges, connection dimensions in accordance with JIS B 2220 BL, raised face RF



Flange ^{1) 2) 3)}	Slange ^{1) 2) 3)}							Diaphragm seal	Option		
Nominal diameter	Nominal pressure	D	b	g	Number	g ₂	k	weight			
		[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]	HP ⁴⁾	LP ⁵⁾	
50 A	10 K	155	16	96	4	19	120	2.3 (5.07)	Х	TK	
80 A	10 K	185	18	126	8	19	150	3.5 (7.72)	1	TL	
100 A	10 K	210	18	151	8	19	175	4.7 (10.36)	4	ТМ	

1) Material: AISI 316L

2) The roughness of the surface in contact with the medium, including the raised face of the flanges (all standards) made of Alloy C276, Monel, tantalum or PTFE, is $R_a < 0.8 \mu m$ (31.5 μin). Reduced surface roughness available on request.

3) The raised face of the flange is made of the same material as the process membrane.

4) Product Configurator, order code for "Process connection, HP/ HP+LP:"

5) Product Configurator, order code for "Alternative process connection LP side:"

Maximum diameter of membrane $Ød_M$

A ¹⁾	K ²⁾			Ød _M (n	nm)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
50 A	10 K	-	52	62	60	59	-
80 A	10 K	-	80	-	-	-	-
100 A	10 K	-	80	-	-	-	-

1) Alphanumeric designation of the flange size.

2) Alphanumeric pressure rating of a component.

Process connections FMD77 with diaphragm seal, low-	Process connection low-pressure side	Material	Seal	Option ¹⁾
pressure side	Mounting: 7/16 – 20 UNF, Process isolatir	ng diaphragm	low-pressure side AISI 316L	
	1/4 - 18 NPT IEC 61518	C22.8	FKM Viton	В
	1/4 - 18 NPT IEC 61518,	AISI 316L	FKM Viton	D
	1/4 - 18 NPT IEC 61518	Alloy C276	FKM Viton	F
	1/4 - 18 NPT IEC 61518	AISI 316L	PTFE+C4-ring	Н

Process connection low-pressure side	Material	Seal	Option ¹⁾
1/4 - 18 NPT IEC 61518	Alloy C276	PTFE+C4-ring	J
1/4 - 18 NPT IEC 61518	AISI 316L	EPDM	К
1/4 - 18 NPT IEC 61518	Alloy C276	EPDM	L
1/4 - 18 NPT IEC 61518	AISI 316L	Kalrez	М
1/4 - 18 NPT IEC 61518	Alloy C276	Kalrez	N
1/4 – 18 NPT IEC 61518	AISI 316L	Chemraz	Р
1/4 - 18 NPT IEC 61518	Alloy C276	Chemraz	Q
1/4 - 18 NPT IEC 61518	AISI 316L	FKM Viton, cleaned from oil and grease	S
1/4 – 18 NPT IEC 61518	AISI 316L	FKM Viton, cleaned for oxygen service	Т
RC 1/4	AISI 316L	FKM Viton	U
LP diaphragm seal and capillary	AISI 316L	welded	1

1) Product Configurator, order code for "Process connection, LP side; seal:"

FMD78: Selecting the process
connection and capillary lineThe device can be fitted with different process connections on the high-pressure side (HP) and on
the low-pressure side (LP).

The FMD78 can also be fitted with different capillary lengths on the high-pressure side (HP) and on the low-pressure side (LP).

When using diaphragm seal systems with a capillary, sufficient strain relief must be provided to prevent the capillary from bending (capillary bending radius \geq 100 mm (3.94 in)).

Example:


- Process connection on high-pressure side = DN80 flange
- Process connection on low-pressure side = DN50 flange
- Capillary length on high-pressure side = 2 m (6.6 ft)
- Capillary length on low-pressure side = 5 m (16 ft)

Your benefits:

- Thanks to the variety of order options, the devices can be optimally adapted to the given installation situation
- Reduced costs due to optimum system design
- Easier installation due to adjusted length of capillary on low-pressure side and high-pressure side
- Easier adaptation to existing installation situations


Ordering information:

- Process connections are indicated in the relevant section by HP (high-pressure side) and LP (low-pressure side)
- Order details for capillary lengths $\rightarrow \square 91$



Due to the use of different process connections and capillary lines, it is essential that the device be designed/ordered using the "Applicator Sizing Diaphragm Seal" selection tool, which is available free of charge. Additional information can be found in the "Planning instructions, diaphragm seal systems" section → 🖺 100


FMD78 basic device



Process connections FMD78 with diaphragm seal

- The following drawings are schematic diagrams. In other words, the dimensions of a diaphragm seal supplied may deviate from the dimensions specified in this document.
 - Observe the information in the "Planning instructions for diaphragm seal systems" section $\Rightarrow \cong 100$
 - For further information please contact your local Endress+Hauser Sales Center.

Pancake seal



Flange					Diaphragm seal	1) 2)	Option	L
Material	Nominal diameter	Nominal pressure ³⁾	D	b	Weight of two diaphragm seals	1		
					[kg (lb)]	1	HP ⁴⁾	LP ⁵⁾
			[mm]	[mm]				
	DN 50	PN 16-400 ⁶⁾	102	20 - 22	2.6 (5.73)	-	UF 7)	UL
	DN 80	PN 16-400 ⁶⁾	138	20 - 22	4.6 (10.14)	-	UH 7)	UM
	DN 100	PN 16-400 ⁶⁾	162	20 - 22	6.2 (13.67)	-	UJ	UN
AISI 316L	[in]	[lb/sq.in]	[in]	[in]				
	2	150-2500	3.9	0.79 - 0.87	2.6 (5.73)	CRN	VF 7)	UP
	3	150-2500	5	0.79 - 0.87	4.6 (10.14)	CRN	VH 7)	UR
	4	150-2500	6.22	0.79 - 0.87	6.2 (13.67)	CRN	VJ	US

1) Approval

2) CSA approval: Product Configurator, order code for "Approval"

3) The specified nominal pressure applies to the diaphragm seal. The maximum pressure for the measuring device is dependent on the lowest-rated element, with regard to pressure, of the selected components → 🗎 45.

4) Product Configurator, order code for "Process connection, HP/ HP+LP:"

5) Product Configurator, order code for "Alternative process connection LP side:"


6) With PTFE coating, maximum working pressure = 250 bar (3625 psi), for details see "Application range of PTFE film" → 🗎 41

7) With TempC Membrane

Maximum diameter of membrane $Ød_M$

DN	PN		Ød _M (mm)									
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE					
50	16-400	61	58	62	60	59	52					
80	16-400	89	89	90	92	89	80					
100	16-400	-	89	90	92	89	-					


NPS	Class		Ød _M (in)									
in		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE					
2	150-2500	2.40	2.05	2.32	2.36	2.32	2.05					
3	150-2500	3.50	3.50	3.54	3.62	3.50	3.14					
4	150-2500	-	3.14	3.50	3.62	3.50	-					



Item	Designation	ion Material M		Nominal pressure	Weight	Option ¹⁾
			[bar (psi)]		[kg (lb)]	
A	Threaded, ISO 228 G ½ A EN837 with PTFE seal -40 to +260 °C (-40 to +500 °F)	AISI 316L,	≤ 40 (580)	PN 40	1.43 (3.15)	GA ²⁾
В	Threaded, ANSI ½ MNPT with PTFE seal -40 to +260 °C (-40 to +500 °F)	screws made of A4				RL ²⁾

1) Product Configurator, order code for "Process connection, HP/ HP+LP:"


2) In combination with silicone oil, inert oil and vegetable oil.



Item	Designation	Material	Measuring range	Nominal pressure	Weight	Option ¹⁾
			[bar (psi)]		[kg (lb)]	
A	Threaded, ISO 228 G $\frac{1}{2}$ A EN837 with metal seal (silver-plated) –60 to +400 °C (–76 to +752 °F)	AISI 316L,	≤ 40 (580)	PN 40	1.38 kg (3.0/1b)	GA ²⁾
В	Threaded, ANSI $\frac{1}{2}$ MNPT with metal seal (silver-plated) -60 to +400 °C (-76 to +752 °F)	screws made of A4				RL ²⁾

1) Product Configurator, order code for "Process connection"

2) In combination with high-temperature oil.




Item	Designation	Material	Measuring range	Nominal pressure	Weight	Option ¹⁾
			[bar (psi)]		[kg (lb)]	
A	Threaded, ISO 228 G $\frac{1}{2}$ A EN837 with metal seal (silver-plated) -60 to +400 °C (-76 to +752 °F)	AISI 316L,	≤ 40 (580)	PN 40	1.38 kg (3.04 lb)	GA ²⁾
В	Threaded, ANSI $\frac{1}{2}$ MNPT with metal seal (silver-plated) -60 to +400 °C (-76 to +752 °F)	screws made of A4				RL

Product Configurator, order code for "Process connection" In combination with high-temperature oil. 1)


2)

With TempC process membrane



Item	Designation	Material	Measuring range	PN	Weight	Option ¹⁾
			bar (psi)		kg (lb)	
А	Threaded, ISO 228 G ¹ / ₂ EN 837 with metal seal (silver-plated) -60 to $+400$ °C (-76 to $+752$ °F)	AISI 316L	≤ 40 (580)	PN 40	2.35 kg (5.18 lb)	GA
В	Threaded, ASME MNPT $\frac{1}{2}$ with metal seal (silver-plated) -60 to +400 °C (-76 to +752 °F)	Screws made of A4	≤ 40 (000)	r in 40	2.35 kg (5.18 lb)	RL

Product Configurator, "Process connection" ordering feature 1)




Material 1)	Nominal pressure	d _M		Weight	Option	
		Standard	With TempC Membrane			
		[mm]	[mm]	[kg (lb)]	HP ²⁾	LP ³⁾
AISI 316L	PN 25	50	48	0.75 (1.65)	TK ^{4) 5)}	UH ^{4) 5)}

1) Roughness of wetted surfaces $R_a < 0.76 \mu m$ (29.9 μin) as standard.

- Product Configurator, order code for "Process connection, HP/ HP+LP:" 2)
- 3) Product Configurator, order code for "Alternative process connection LP side:"
- 4) 5) Alternatively available with TempC Membrane.
- Including slip-on flange.

Tri-Clamp ISO 2852



Material	Nominal	Nominal	Nominal	C ₇	d _M		h	Weight	Approval	Option	
1	diameter ISO 2852	diameter DIN 32676	diameter		Standard	With TempC Membran e			2)		
			[in]	[mm]	[mm]	[mm]	[mm]	[kg (lb)]		HP ³⁾	LP ⁴⁾
	ND 25 / 33.7	DN 25	1	50.5	24	-	37	0.32 (0.71)	EHEDG, 3A, CRN	ТВ	UA
	ND 38	DN 40	1 ½	50.5	36	36	30	1 (2.21)	EHEDG, 3A, CRN	TC ^{5) 6)}	UB ^{5) 6)}
AISI 316L	ND 51 / 40	DN 50	2	64	48	41	30	1.1 (2.43)	EHEDG, 3A, CRN	TD ^{5) 6)}	UC ⁵⁾⁶⁾
	ND 63.5	DN 50	2 1/2	77.5	61	61	30	0.7 (1.54)	EHEDG, 3A	TE ⁷⁾	UD ⁷⁾
	ND 76.1	-	3	91	73	61	30	1.2 (2.65)	EHEDG, 3A, CRN	TF ⁶⁾	UE ⁶⁾

1) Roughness of wetted surfaces $R_a < 0.76 \mu m$ (29.9 μin) as standard. Lower surface roughness on request.


2) CSA approval: Product Configurator, order code for "Approval"

3) Product Configurator, order code for "Process connection, HP/ HP+LP:"


4) Product Configurator, order code for "Alternative process connection LP side:"

5) Optionally available as ASME-BPE-compliant diaphragm seal version for use in biochemical processes, surfaces in contact with medium R_a < 0.38 μm (15 μin)), electropolished; order using the order code for "Additional options 1" or "Additional options 2", option "O" in the order code.
 6) Alternatively available with TempC Membrane.

7) With TempC Membrane



SMS nozzles with coupling nut



Material		Nominal	D	f	G	m	h	d _M	Weight	Approval	Option	
-)		pressure	[mm]	[mm]		[mm]	[mm]	[mm]	[kg (lb)]		HP ²⁾	LP ³⁾
AISI	1 1⁄2	PN 25	74	4	Rd 60 - 1/6	25	57	36	0.65 (1.43)	3A	TH ⁴⁾	UF ⁴⁾
316L	2	PN 25	84	4	Rd 70 – 1/6	26	62	48	1.05 (2.32)	3A	TI ⁴⁾	UG ⁴⁾


1) Surface roughness of the wetted surfaces $R_a < 0.76 \ \mu m$ (29.9 μin) as standard.

2) Product Configurator, order code for "Process connection, HP/ HP+LP:"

3) Product Configurator, order code for "Alternative process connection LP side:"

4) With TempC Membrane

Hygienic connection, sanitary tank spud, barrel (extended diaphragm seal) 2"



Material ¹⁾	erial ¹⁾ Weight kg (lbs)		Option ²⁾	
AISI 316L	2.5 (5.51)	3A	WH ^{3) 4)}	


1) Surface roughness of the wetted surfaces $R_a < 0.76 \ \mu m$ (29.9 μin) as standard. Lower surface roughness on request.

2) Product Configurator, order code for "Process connection, HP/ HP+LP:"

3) With TempC Membrane

4) EPDM seal enclosed

Taper adapter with slotted-nut, DIN 11851



Material	Taper ada	pter			Slotted-nu	ıt	Diaphragr	n seal		Approval	Option	
1)							d _M		Weight	1		
	Nominal diameter	Nominal pressure	D	f	G	m	Standard	with TempC Membra ne	-			
		[bar]	[mm]	[mm]		[mm]	[mm]	[mm]	[kg (lb)]		HP ²⁾	LP ³⁾
	DN 32	PN 40	50	10	Rd 58 x 1/6"	21	32	28	0.45 (0.99)	3A, EHEDG	MI ⁴⁾	TP ⁴⁾
	DN 40	PN 40	56	10	Rd 65 x 1/6"	21	38	36	0.45 (0.99)	3A, EHEDG	MZ ⁴⁾	TU ⁴⁾
AISI 316L	DN 50	PN 25	68.5	11	Rd 78 x 1/6"	19	52	48	1.1 (2.43)	3A, EHEDG	MR ⁵⁾	TR ⁵⁾
	DN 65	PN 25	86	12	Rd 95 x 1/6"	21	66	61	2.0 (4.41)	3A, EHEDG	MS ⁵⁾	TS ⁵⁾
	DN 80	PN 25	100	12	Rd 110 x 1/4"	26	81	61	2.55 (5.62)	3A, EHEDG	MT ⁵⁾	TT ⁵⁾


1) Surface roughness of the wetted surfaces $R_a < 0.76~\mu m$ (29.9 $\mu in)$ as standard.

2) Product Configurator, order code for "Process connection, HP/ HP+LP:"

3) Product Configurator, order code for "Alternative process connection LP side:"

4) with TempC Membrane

5) Alternatively available with TempC Membrane.



Material 1)	Designation	Nominal pressure	D	d _M		Weight	Approval	Option	n
				Standard	with TempC membrane				
			[mm]	[mm]	[mm]	[kg (lb)]		HP ²⁾	LP ³⁾
AISI 316L	Type F for pipes DN 25 - DN 32	PN 40	50	34	36	0.4 (0.88)	EHEDG, 3A	TU ⁴⁾	UK ⁴⁾
AISI 316L	Type N for pipes DN 40 - DN 162	PN 40	68	58	61	0.8 (1.76)	EHEDG, 3A	TR ⁵⁾	-


1) Surface roughness of the wetted surfaces $R_a < 0.76 \ \mu m$ (29.9 μin) as standard.

2) Product Configurator, order code for "Process connection, HP/ HP+LP:"


3) Product Configurator, order code for "Alternative process connection LP side:"

4) With TempC membrane

5) Alternatively available with TempC membrane.



NEUMO BioControl



Material ¹⁾		O BioCo ss tempe		range: -	-10 to +20	0 °C (+1	l4 to +3	92 °F))	Diaphragi d _M	m seal	Weight	Approval	Optio	n
	DN 2)	$DN^{2} PN^{3} D d d_2 d_3 d_1 h$					h	Standard	With TempC Membrane					
		[bar] [mm] [mm] [mm] [mm] [mm] [mm]					[mm]	[mm]	[mm]	[kg (lb)]		HP ⁴⁾	LP ⁵⁾	
AICI 21/1	DN 50	PN 16	90	-	4 x Ø 9	50	70	27	40	36	1.1 (2.43)	3A	S4 ⁶⁾	TV
AISI 316L	DN 80	PN 16	140	25	4 x Ø 11	87.4	115	37	61	61	2.6 (5.73)	3A	S6 ⁶⁾	TW

1) Roughness of wetted surfaces R_a < 0.76 μm (29.9 $\mu in)$ as standard.

2) Nominal diameter


Nominal pressure 3)

4)

Product Configurator, order code for "Process connection, HP/ HP+LP:" Product Configurator, order code for "Alternative process connection LP side:" 5)

With TempC Membrane 6)

Universal process adapter



- The roughness of the surface in contact with the medium R_a < 0.76 μm (30 $\mu in)$
- Temperature operating range: -60 to +150 °C (-76 to +302 °F)
- Silicone molded seal: FDA 21CFR177.2600/USP Class VI, order number: 52023572

Designation	Nominal pressure	Weight	Approval	Option	
		[kg (lb)]	1	HP ¹⁾	LP ²⁾
Universal process adapter Molded seal made of silicone (4)	PN 10	0.8 (1.76)	3A	00 ³⁾	UT


1) Product Configurator, "Process connection, HP/HP+LP:" ordering feature

2) Product Configurator, "Alternative process connection LP side:" ordering feature

3) With TempC membrane.

Process connections FMD78 with diaphragm seal

EN flanges, connection dimensions in accordance with EN 1092-1 / JIS flanges, connection dimensions in accordance with JIS B 2220 BL



Flange ¹⁾	2) 3)						Boltholes			Diaphragm seal	Option	
4)	Nominal pressure	Туре	D	b	g	f	Number	g ₂	k	Weight	1	
			[mm]	[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]	HP ⁵⁾	LP ⁶⁾
DN 50	PN 10-40	B1	165	20	102	3	4	18	125	3.0 (6.62)	B3 ^{7) 8)}	TA ^{7) 8)}
DN 80	PN 10-40	B1	200	24	138	3.5	8	18	160	5.3 (11.69)	B5 ^{7) 8)}	TB ^{7) 8)}
DN 100	PN 10-16	B1	220	20	158	4	8	18	180	4.5 (9.92)	BT	TC
DN 100	PN 25-40	B1	235	24	162	5	8	22	190	7 (15.44)	B6	TD

1) Material: AISI 316L

2) The roughness of the surface in contact with the medium, including the raised face of the flanges (all standards) made of Alloy C276, Monel, tantalum, gold or PTFE, is R_a< 0.8 µm (31.5 µin). Reduced surface roughness available on request.</p>

3) The raised face of the flange is made of the same material as the process membrane.

4) Nominal diameter

5) Product Configurator, order code for "Process connection, HP/ HP+LP:"

6) Product Configurator, order code for "Alternative process connection LP side:"

7) Alternatively available with TempC membrane.

8) Alternatively available with gold-coated TempC membrane (Product Configurator, order code for "Membrane material" option "G").

Flange ¹) 2) 3)					Boltholes			Diaphragm seal	Option	
4)	Nominal pressure					Number	g ₂	k	Weight]	
		[mm]	[mm]	[mm]	[mm]		[mm]	[mm]	[kg (lb)]	HP ⁵⁾	LP ⁶⁾
50 A	10 K	155	16	96	2	4	19	120	2.3 (5.07)	KF	TK
80 A	10 K	185	18	127	2	8	19	150	3.3 (7.28)	KL	TL
100 A	10 K	210	18	151	2	8	19	175	4.4 (9.7)	КН	ТМ

1) Material: AISI 316L

2) The roughness of the surface in contact with the medium, including the raised face of the flanges (all standards) made of Alloy C276, Monel, tantalum or PTFE, is $R_a < 0.8 \ \mu m$ (31.5 μ in). Reduced surface roughness available on request.

3) The raised face of the flange is made of the same material as the process membrane.

4) Nominal diameter

5) Product Configurator, order code for "Process connection, HP/ HP+LP:"

6) Product Configurator, order code for "Alternative process connection LP side:"

Maximum diameter of membrane $\mathcal{O}d_M$

DN	PN			Ød _M (r	nm)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
DN 50	PN 10-40	61	58	57	60	59	52
DN 80	PN 10-40	89	89	89	92	89	80
DN 100	PN 10-16	-	80	90	92	89	-
DN 100	PN 25-40	-	80	90	92	89	-

Maximum diameter of membrane $Ød_M$


A 1)	K ²⁾			Ød _M (n	nm)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)	PTFE
50 A	10 K	-	52	62	60	59	-
80 A	10 K	-	80	-	-	-	-
100 A	10 K	-	80	-	-	-	-

1) Alphanumeric designation of the flange size.

2) Alphanumeric pressure rating of a component.

Process connections FMD78 E with diaphragm seal 1

EN flanges with extended diaphragm seal, connection dimensions in accordance with EN 1092-1 $\,$



Flange	1) 2)							Boltholes			Diaphragm	ı seal	Option ³⁾
4)	Nominal pressure	Туре	D	b	g	L	d ₃	Number	g ₂	k	d _M [mm]	Weight	(HP + LP)
			[mm]	[mm]	[mm]	[mm]	[mm]		[mm]	[mm]		[kg (lb)]	
DN 80	PN 10-40	B1	200	24	138	50	76	8	18	160	72	6.2 (13.67)	D4
						100	1					6.7 (14.77)	
						200						7.8 (17.20)	

1) Material: AISI 316L


In the case of process isolating diaphragms made of Alloy C276, Monel oder tantalum, the raised face of the flange and the barrel pipe are made 2) of 316L. Product Configurator, order code for "Process connection, HP/ HP+LP:"

3)

4) Nominal diameter

Process connections FMD78 with diaphragm seal

ASME flanges, connection dimensions as per ASME B 16.5, raised face RF



Flange ^{1) 2) 3)}						Bol	tholes		Diaphragm seal	4) 5)	Option	
Nominal diameter	Class	D	b	g	f	6)	g ₂	k	Weight	1		
[in]	[lb./sq.in]	[in]	[in]	[in]	[in]	1	[in]	[in]	[kg (lb)]	1	HP ⁷⁾	LP ⁸⁾
2	150	6	0.75	3.62	0.06	4	0.75	4.75	2.2 (4.85)	CRN	AF 9) 10)	TE ^{9) 10)}
2	300	6.5	0.88	3.62	0.06	8	0.75	5	3.4 (7.5)	CRN	AR ^{9) 10)}	TF ^{9) 10)}
2	400/600	6.5	1	3.62	0.25	8	0.75	5	4.3 (9.48)	-	AJ	-
3	150	7.5	0.94	5	0.06	4	0.75	6	5.1 (11.25)	CRN	AG 9) 10)	TG ^{9) 10)}
3	300	8.25	1.12	5	0.06	8	0.88	6	7.0 (15.44)	CRN	AS ^{9) 10)}	TH ^{9) 10)}
4	150	9	0.94	6.19	0.06	8	0.75	7.5	7.2 (15.88)	CRN	AH	TI
4	300	10	1.25	6.19	0.06	8	0.88	7.88	11.7 (25.8)	CRN	AT	TJ

Material AISI 316/316L: Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual-rated)
 The roughness of the surface in contact with the medium, including the raised face of the flanges (all standards) made of Alloy C276, Monel,

tantalum, gold or PTFE, is R_a < 0.8 μ m (31.5 μ in). Reduced surface roughness available on request.

3) The raised face of the flange is made of the same material as the process membrane.

- 4) Approval
- 5) CSA approval: Product Configurator, order code for "Approval"
- 6) Number

7) Product Configurator, order code for "Process connection, HP/ HP+LP:"


8) Product Configurator, order code for "Alternative process connection LP side:"

9) Alternatively available with TempC membrane.

10) Alternatively available with gold-coated TempC membrane (Product Configurator, order code for "Membrane material" option "G").

NPS	Class			Ød _M (in)		
		316L TempC	316L	Alloy C276	Tantalum	Monel (Alloy 400)
2	150	2.40	-	2.44	2.44	2.44
2	300	2.40	-	2.44	2.44	2.44
2	400/600	-	2.05	2.44	2.44	2.44
3	150	3.50	-	3.62	3.62	3.62
3	300	3.50	-	3.62	3.62	3.62
4	150	-	3.15	3.62	3.62	3.62
4	300	-	3.15	3.62	3.62	3.62

Maximum diameter of membrane $Ød_M$



ASME flanges with barrel (extended diaphragm seal), connection dimensions in accordance with ASME B 16.5, raised face RF

Flange ^{1) 2)}										gm seal	3) 4)	Option ⁵⁾
Nominal diameter Class D b g f						6)	g ₂	k	d _M	Weight		(HP + LP)
[in]	[lb./sq.in]	[in]	[in]	[in]	[in]	1	[in]	[in]	[in]	[kg (lb)]		
3	150	7.5	0.94	5	0.06	4	0.75	6	2.83	7)	CRN	J4 ⁷⁾
4	150	9	0.94	6.19	0.06	8	0.75	7.5	3.5	7)	CRN	J5 ⁷⁾

1) Material: AISI 316/316L. Combination of AISI 316 for required pressure resistance and AISI 316L for required chemical resistance (dual-rated)

2) In the case of process membranes made of Alloy C276, Monel or tantalum, the raised face of the flange and the barrel pipe are made of 316L.

3) Approval

4) CSA approval: Product Configurator, order code for "Approval"


5) Product Configurator, order code for "Process connection, HP/ HP+LP:"


6) Number

7) Choice of 2", 4", 6" or 8" barrel (extended diaphragm seal), for diameter and weight of barrel (extended diaphragm seal) see the following table

Option ¹⁾	Nominal diameter	Class	(L)	d ₃	Weight
	[in]	[lb./sq.in]	in (mm)	in (mm)	[kg (lb)]
J4	3	150	2 (50.8) / 4 (101.6) / 6 (152.4) / 8 (203.2)	2.99 (76)	6.0 (13.2) / 6.6 (14.5) / 7.1 (15.7) / 7.8 (17.2)
J5	4	150	2 (50.8) / 4 (101.6) / 6 (152.4) / 8 (203.2)	3.7 (94)	8.6 (19) / 9.9 (21.8) / 11.2 (24.7) / 12.4 (27.3)

1) Product Configurator, order code for "Process connection"






Item	Designation	Weight in kg (lb)	Option ¹⁾	
		Housing (T14 or T17)	Mounting bracket	
A	Dimensions with T14 housing, optional side display	→ 🗎 47	0.5 (1.10)	U
В	Dimensions with T17 housing, optional side display		0.5 (1.10)	0

1) Product Configurator, order code for "Additional options 2", version "G"

Also available for order as a separate accessory: part number 71102216

Flushing rings



Use flushing rings if there is a risk of medium buildup or clogging at the process connection. The flushing ring is fitted between the process connection and the process connection provided by the customer.

Using the two lateral flushing holes, medium buildup or clogging in front of the process isolating diaphragm can be rinsed away and the pressure chamber vented.

Various nominal widths and forms allow adaption to the respective process flange.

For other details (dimension, weight, materials), see SD01553P/00/EN "Mechanical accessories for pressure measuring devices".

Order options

Flushing rings can be ordered as a separate accessory or as an order option for the device.

Material		Approval ¹⁾	Accessory ²⁾	Order opt	Order option ^{3) 4)}	
		Part number	FMD77	FMD78 ⁵⁾		
	EN1092-1					
	DN25	-	71377379	-	-	
	DN50	-	71377380	PP	PP	
AISI 316L	DN80	-	71377383	PQ	PQ	
AISI 510L	ASME B16.5	·		·		
	NPS 1"	-	71377369	-	-	
	NPS 2"	CRN	71377370	PL	PL	
	NPS 3"	CRN	71377371	PM	PM	

1) CSA approval: Product Configurator, order code for "Approval"

2) Inspection certification according to EN10204-3.1 material

3) Product Configurator order code for "Accessories enclosed"

4) Certificates ordered with the equipment (3.1 material certificate and NACE declaration of conformity and PMI tests) apply to the transmitters and flushing rings listed in the table.

Endress+Hauser offers additional flushing rings as Technical Special Products (TSP).

Component part	Weight
Housing	See "Housing" section
Process connection	See "Process connections" section
Capillary with armoring made of AISI 316L (1.4404)	0.16 kg/m (0.35 lb/m) + 0.2 kg (0.44 lb) (weight per capillary line)
Capillary with armoring made of AISI 316L (PVC)	0.21 kg/m (0.46 lb/m) + 0.2 kg (0.44 lb) (weight per capillary line)
Capillary with armoring made of AISI 316L (PTFE)	0.29 kg/m (0.64 lb/m) + 0.2 kg (0.44 lb) (weight per capillary line)


Weight


⁵⁾ Scope of delivery: 2 x

Materials not in contact with process

ith Transmitter housing








Item number	Component	Material
1	T14 and T15 housing, RAL 5012 (blue)	 Die-cast aluminum with protective powder-coating on polyester base Coating on thread: Heat-curing lubricant varnish
1	T14 housing	Precision casting AISI 316L (1.4435)Coating on thread: Heat-curing lubricant varnish
2	Cover, RAL 7035 (gray)	Die-cast aluminum with protective powder-coating on polyester base
		Precision cast AISI 316L (1.4435) (cover made of 316L if T14 housing made of 316L)
4	Nameplates	 AISI 316L (1.4404), if T14 housing is precision-cast Anodized aluminum, if housing T14/T15 of die-cast aluminum
5	Pressure compensation filter	AISI 316L (1.4404) and PBT-FR
6	Pressure compensation filter, O- ring	VMQ or EPDM
7	Sight glass	Mineral glass
8	Sight glass seal	Silicone (VMQ)
9	Screw	A4
10	Sealing ring	EPDM
11	Snap ring	PA66-GF25
12	Snap ring for nameplates	AISI 304 (1.4301)/ AISI 316 (1.4401)
13	External ground terminal	AISI 316L (1.4404)
14	Cover clamp	Clamp AISI 316L (1.4435), screw A4


Item number	Component	Material
15	Cable entry	Polyamide (PA) or CuZn nickel-plated
16	Seal of cable entry and plug	Silicone (VMQ)
17	Plug T15 housing	PBT-GF30 FR, for dust ignition-proof and Exd: AISI 316L (1.4435)
	Plug T14 housing	 Non-Ex and Ex ia: PBT-GF30 FR All other versions: Housing made of die-cast aluminum: Plug made of die-cast aluminum Housing made of precision casting AISI 316L (1.4435): Plug made of precision casting AISI 316L (1.4435)
18	External operation (keys and key cover), RAL 7035 (gray)	Polycarbonate PC-FR, screw A4




Item number	Component	Material	
1	T17 housing	- AISI 316L (1.4404)	
2	Cover	ADI 510L (1.4404)	
3	Cover seal	EPDM	
4	Nameplates	Lasered on	
5	Pressure compensation filter	AISI 316L (1.4404) and PBT-FR	
6	Pressure compensation filter, O-ring	VMQ or EPDM	
7	Sight glass for non-hazardous area, ATEX Ex ia, NEPSI Zone 0/1 Ex ia, IECEx Zone 0/1 Ex ia, FM NI, FM IS, CSA IS	Polycarbonate (PC)	
8	Sight glass for ATEX 1/2 D, ATEX 1/3 D, ATEX 1 GD, ATEX 1/2 GD, ATEX 3 G, FM DIP, CSA dust ignition-proof	Mineral glass	
9	Sight glass seal	EPDM	
10	Screw	A2-70	
11	Sealing ring	EPDM	
12	Snap ring	PA6	
13	Screw	A4-50 Coating on thread: Heat-curing lubricant varnish	
14	External ground terminal	AISI 316L (1.4404)	
15	Cable entry	Polyamide PA, for dust ignition-proof: CuZn nickel-plated	

Item number	Component	Material
16	Seal of cable entry and plug	Silicone (VMQ)
17	Plug	PBT-GF30 FR, for dust ignition-proof: AISI 316L (1.4435)

Connecting parts




Item number	Component	Material
1	Mounting bracket	Bracket AISI 316L (1.4404)
2		Screw and nuts A4-70
3		Half-shells: AISI 316L (1.4404)
4	Seal for cable from separate housing	EPDM
5	Gland for cable from separate housing	AISI 316L (1.4404)
6	PE cable for separate housing	Abrasion-resistant cable with Dynema strain-relief members; shielded with aluminum-coated film; insulated with polyethylene (PE-LD), black; copper wires, twisted, UV-resistant
7	FEP cable for separate housing	Abrasion-resistant cable; shielded with galvanized steel wire netting; insulated with fluorinated ethylene propylene (FEP), black; copper wires, twisted, UV- resistant
8	Process connection adapter for separate housing	AISI 316L (1.4404)



Item number	Component	Material
1	Connection between the housing and process connection	AISI 316L (1.4404)
2	Screws and nuts	PMD75 PN 160, FMD77, FMD78: • Hexheaded bolt DIN 931-M12x90-A4-70 • Hexheaded nut DIN 934-M12-A4-70
		PMD75 PN 420: • Hexheaded bolt ISO 4014-M12x90-A4 • Hexheaded nut ISO 4032-M12-A4-bs
3	Cell body	AISI 316L (1.4404)
4	Setscrew	DIN 915 M 6x8 A2-70
5	Bearing	DIN 5401 (1.3505)
6	Temperature isolator	AISI 316L (1.4404)
7	Side flanges	1.4408 / CF3M ¹⁾ / AISI 316L
8	U-bracket	AISI 304 (1.4301)
9	Heat-shrink tube (available only if flexible armor for capillary has PVC coating or PTFE hose)	Polyolefin

1) Cast equivalent to material AISI 316L



Item	Component	A Standard ¹⁾ Armor for capillary	B PVC-coated Armor for capillary	C PTFE hose Armor for capillary
1	Capillary	AISI 316 Ti (1.4571)	AISI 316 Ti (1.4571)	AISI 316 Ti (1.4571)
2	Protective hose for capillary	AISI 316L (1.4404) ²⁾	AISI 316L (1.4404)	AISI 316L (1.4404)
3	Coating/armor	-	PVC ³⁾	PTFE ⁴⁾
4	Single-ear clamp	-	-	1.4301
5	Shrink tubing at capillary junction	-	Polyolefin	-

1) If no option is specified when ordering, order option "SA" is supplied.

2) Product Configurator, order code for "Armor for capillary:" option "SA"

3) Product Configurator, order code for "Armor for capillary:" option "SB"

4) Product Configurator, order code for "Armor for capillary." option "SC"

Materials in contact with	NOTICE
process	► The device components in contact with the process are specified in the "Mechanical construction"
	$\rightarrow \cong$ 46 and "Ordering information" $\rightarrow \cong$ 113 sections.

Delta-ferrite content

A delta-ferrite content of \leq 3% can be guaranteed and certified for the wetted parts of the FMD78 if option "8" is selected in the "Additional options 1" or "Additional options 2" order code in the Product Configurator.

TSE Certificate of Suitability (Transmissible Spongiform Encephalopathy)

The following applies to all device components in contact with the process:

- They do not contain any materials derived from animals.
- No additives or operating materials derived from animals are used in production or processing.

Process connections

- "Clamp connections" and "Hygienic process connections": AISI 316L (DIN/EN material number 1.4435)
- Endress+Hauser supplies DIN/ EN process connections with threaded connections made of stainless steel as per AISI 316L (DIN/EN material number 1.4404 or 14435). With regard to their stability-temperature property, the materials 1.4404 and 1.4435 are grouped together under 13EO in EN 1092-1: 2001 Tab. 18. The chemical composition of the two materials can be identical.
- Some process connections are also available in alloy C276 (DIN/EN material number 2.4819). For this purpose see the information in the "Mechanical construction" section.
- Side flanges: 316L, C 22.8 with zinc plating or alloy C 276. The C22.8 side flanges are coated with anti-corrosion protection (zinc, chrome). To prevent the formation of hydrogen and thereby diffusion through the membrane, Endress+Hauser recommends the use of 316L side flanges for applications involving water. Hydrogen diffusion through the membrane leads to measurement errors, or in extreme cases to a device failure.

Process isolating diaphragm

Sensor	Designation	Option ¹⁾		
	AISI 316L, TempC, high-pressure side (HP)	Е		
	AISI 316L with gold coating (25 μm), TempC, high-pressure side (HP) $^{2)}$	D		
	AISI 316L, high-pressure side (HP)	1		
FMD77	Alloy C 276, high-pressure side (HP) ³⁾	2		
FIND//	Monel (2.4360), high-pressure side (HP) ³⁾	3		
	Tantalum (UNS R05200), high-pressure side (HP) ³⁾	5		
	AISI 316L with gold-rhodium coating, high-pressure side (HP)			
	AISI 316L with 0.25 mm (0.01 in)PTFE coating, high-pressure side (HP)	8		
	AISI 316L, TempC, high-pressure side (HP) + low-pressure side (LP)	F		
	AISI 316L with gold coating (25 μm), TempC, high-pressure side (HP) + low-pressure side (LP) $^{2)}$	G		
	AISI 316L, high-pressure side (HP) + low-pressure side (LP)	Н		
FMD77 with capillaries on	AISI C 276, high-pressure side (HP) + low-pressure side (LP)			
low-pressure side (LP)	Monel (2.4360), high-pressure side (HP) + low-pressure side (LP)	К		
	Tantalum (UNS R05200), high-pressure side (HP) + low-pressure side (LP)			
	AISI 316L with gold-rhodium coating, high-pressure side (HP) + low-pressure side (LP)	М		
	AISI 316L with 0.25 mm (0.01 in)PTFE coating, high-pressure side (HP) + low-pressure side (LP)			
	AISI 316L with gold coating (25 μm), TempC $^{2)}$			
	AISI 316L, TempC			
	AISI 316L	1		
	Alloy C 276 ³⁾	2		
FMD78	Monel (2.4360) ³⁾	3		
	Tantalum (UNS R05200) ³⁾	5		
	AISI 316L with gold-rhodium coating	6		
	AISI 316L with 0.25 mm (0.01 in) PTFE foil (FDA 21 CFR 177.1550)	8		
	AISI 316L	1		
	Alloy C 276 (2.4819)	2		
PMD75	Monel (2.4360)	3		
	Tantalum (UNS R05200)	5		
	Alloy C 276 with gold-rhodium coating	6		

Product Configurator, order code for "Membrane material" The TempC gold-plated membrane does not offer corrosion protection! 1) 2)

The material used in the raised face of the flange is the same as that used in the process isolating diaphragm. For devices with a barrel (extended diaphragm seal), the flange raised face and the barrel pipe are made of 316L. 3)

Seals

Device	Designation	Option ¹⁾
	FKM Viton	А
	PTFE (PN160bar/16MPa/2400psi)	C ²⁾
	PTFE (PN250bar/25MPa/3625psi)	D ²⁾
	NBR	F
	Copper seal ring	Н
PMD75	Copper seal ring, oxygen service, observe pressure and temperature application limits	К
	FKM Viton, cleaned from oil and grease	1
	FKM Viton, cleaned for oxygen service, observe pressure and temperature application limits	2
	PTFE, cleaned for oxygen service, observe pressure and temperature application limits	3
	EPDM	J ³⁾

- Product Configurator, order code for "Seal" 1)
- Suitable for foodstuffs FDA21 CFR 177.1550
- 2) 3) Suitable for drinking water NSF61.

Fill fluid

FMD77: Fill fluid of diaphragm seal

Process connection	Designation	Option ^{1) 2)}
High-pressure side (HP)	Silicone oil (food-safe FDA 21 CFR 175.105)	А
	Vegetable oil (food-safe FDA 21 CFR 172.856)	D
	Inert oil	F
	Low-temperature oil	L
	High-temperature oil	V
Low-pressure side (LP)	m capillary, silicone oil (food-safe FDA 21 CFR 175.105)	М
	m capillary, vegetable oil (food-safe FDA 21 CFR 172.856)	N
	m capillary, inert oil	0
	m capillary; low-temperature oil	Р
	m capillary; high-temperature oil	Q
	ft capillary, silicone oil (food-safe FDA 21 CFR 175.105)	R
	ft capillary, vegetable oil (food-safe FDA 21 CFR 172.856)	S
	ft capillary, inert oil	Т
	ft capillary; low-temperature oil	U
	ft capillary; high-temperature oil	W

Product Configurator, order code for "Fill fluid" 1)

For diaphragm seal devices with 3-A and EHEDG certificates, only select fill fluids with FDA approval! 2)

FMD77: Fill fluid of measuring cell

FMD77	Designation	Option ¹⁾
With capillary on low-pressure side (LP)	Silicone oil	Standard, if no option was selected.
	Inert oil, PWIS-free	НС
Without capillary on low-pressure side (LP)	Silicone oil	Standard, if no option was selected.

FMD77	Designation	Option ¹⁾
	Inert oil, cleaned for oxygen service	HB
	Inert oil, PWIS-free	НС

1) Product Configurator, order code for "Service"

FMD78: Fill fluid of diaphragm seal

Capillary length;	Designation	Option 1
Symmetrical	ft capillary; silicone oil (food-safe FDA 21 CFR 175.105)	A ²⁾
	ft capillary; vegetable oil (food-safe FDA 21 CFR 172.856)	B ²⁾
	ft capillary; high-temperature oil	C 2)
	ft capillary; inert oil, oxygen service, observe pressure/temp. application limits	D ²⁾
	ft capillary; low-temperature oil	E ²⁾
	ft capillary, inert oil	F ²⁾
	m capillary; silicone oil (food-safe FDA 21 CFR 175.105)	12)
	m capillary; vegetable oil (food-safe FDA 21 CFR 172.856)	2 ²⁾
	m capillary; high-temperature oil	3 ²⁾
	m capillary; inert oil, oxygen service, observe pressure/temp. application limits	4 ²⁾
	m capillary; low-temperature oil	5 ²⁾
	m capillary, inert oil	6 ²⁾
Asymmetrical Low pressure side (LP)	m capillary, silicone oil ³⁾ (food-safe FDA 21 CFR 175.105), LP-side	M ²⁾
	m capillary, vegetable oil (food-safe FDA 21 CFR 172.856), LP-side	N ²⁾
	m capillary, inert oil, LP side	O ²⁾
	m capillary, low-temperature oil, LP side	P 2)
	m capillary, high-temperature oil, LP side	Q ²⁾
	ft capillary, silicone oil (food-safe FDA 21 CFR 175.105), LP-side	R ²⁾
	ft capillary; vegetable oil (food-safe FDA 21 CFR 172.856), LP-side	S ²⁾
	ft capillary, inert oil, LP side	T ²⁾
	ft capillary, low-temperature oil, LP side	U ²⁾
	ft capillary, high-temperature oil, LP side	W ²⁾
Asymmetrical	ft capillary, HP side	V ⁵⁾
High pressure side (HP) ⁴ m capillary, HP side	W ⁵⁾

1) For diaphragm seal devices with 3-A and EHEDG certificates, only select fill fluids with FDA approval!

2) Product Configurator, order code for "Fill fluid"

- 3) If the capillary length for asymmetrical LP or HP is identical, select a symmetrical capillary length when ordering.
- 4) If the capillary length for asymmetrical LP or HP is identical, select a symmetrical capillary length when ordering.
- 5) Product Configurator, order code for "Additional options 2"

FMD78: Fill fluid of measuring cell

Designation	Option ¹⁾
Silicone oil	Standard, if no option was selected.
Inert oil, PWIS-free	нс

1) Product Configurator, order code for "Service"

PMD75: Fill fluid of measuring cell

Designation	Option
Silicone oil	Standard, if no option was selected.
Inert oil, FKM Viton, oxygen service	2 ¹⁾
Inert oil, PTFE, oxygen service	3 1)
Inert oil, copper seal ring, oxygen service	K ¹⁾
Inert oil, PWIS-free	HC ²⁾
Inert oil, cleaned for oxygen service	HB ²⁾

1)

Product Configurator, order code for "Seal" Product Configurator, oder code for "Service" 2)

Operability

Operating concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnosis

Quick and safe commissioning

Guided menus for applications

Reliable operation

- Local operation possible in several languages
- Standardized operation at the device and in the operating tools
- Parameters relating to measured values can be locked/unlocked using the device's write protection switch, using the device software or via remote operation

Efficient diagnostics increase measurement availability

- Remedial measures are integrated in plain text
- Diverse simulation options

Local operation

Functions

Function	External operation (operating keys, optional, not T17 housing)	Internal operation (electronic insert)	Onsite display (optional)
Position adjustment (zero point correction)	V	V	v
Setting lower range value and upper range value - reference pressure present at the device	✔ (HART only)	✔ (HART only)	V
Device reset	V	V	~
Locking and unlocking parameters relevant to the measured value		V	V
Value acceptance indicated by the green LED	V	V	~
Switching damping on and off	✓ (only if display is connected)	✓ (HART and PA only)	V
Configuring the bus address of the device (PA)		V	~
Switching simulation mode on and off (FOUNDATION Fieldbus)		~	V

Operating the device using onsite display (optional)

A 4-line liquid crystal display (LCD) is used for display and operation. The onsite display shows measured values, dialog text as well as fault and notice messages in plain text, thereby supporting the user in every stage of operation.

The display can be removed for easy operation.


The device display can be turned in 90° steps.

Depending on the installation position of the device, this makes it easy to operate the device and read the measured value.

Functions:

- 8-digit measured value display including sign and decimal point and bar graph for
 - 4 to 20 mA HART (bar graph from 4 to 20 mA)
 - PROFIBUS PA (bar graph as graphic display of standardized value of AI block)
 - FOUNDATION Fieldbus (bar graph as graphic display of transducer output).
- Simple and complete menu guidance due to breakdown of parameters into several levels and groups
- Menu guidance in up to 8 languages
- Each parameter is given a 3-digit ID number for easy navigation.
- Option for configuring the display according to individual requirements and preferences, such as language, alternating display, display of other measured values such as sensor temperature, contrast setting.
- Comprehensive diagnostic functions (fault and warning message, peak-hold indicators, etc.).
- Rapid and safe commissioning with the Quick Setup menus


Overview



- 1 Operating keys
- 2 Bargraph
- 3 Symbol
- 4 Header
- 5 Parameter ID number

Operating keys on the exterior of the device

With the aluminum housing (T14), the operating keys are located either outside on the housing, under the protection cap or inside on the electronic insert. With the stainless steel housing (T17), the operating keys are always located inside the housing on the electronic insert.



A 4 to 20 mA HART

B PROFIBUS PA and FOUNDATION Fieldbus

The operating keys located externally on the device work on the Hall sensor principle. As a result, no additional openings are required in the device. This guarantees:

- Complete protection against environmental influences such as moisture and contamination.
- Simple operation without any tools.
- No wear.

Ordering information:


Product Configurator, order code for "Output, operation"

Operating keys and elements located internally on the electronic insert

Ordering information:


Product Configurator, order code for "Output, operation"

HART




- 1 DIP switch for locking/unlocking parameters relevant to the measured value
- 2 DIP switch for switching damping on/off
- 3 Green LED to indicate value being accepted
- 4 Operating keys
- 5 Slot for optional display
- 6 Slot for optional HistoROM®/M-DAT

PROFIBUS PA



- 1 DIP switch for locking/unlocking parameters relevant to the measured value
- 2 DIP switch for switching damping on/off
- *3 Green LED to indicate value being accepted*
- 4 Key for position adjustment and device reset
- 5 DIP switch for bus address
- 6 Slot for optional display
- 7 Slot for optional HistoROM®/M-DAT

FOUNDATION Fieldbus



1 DIP switch for locking/unlocking parameters relevant to the measured value

- 2 DIP switch for simulation mode on/off
- *3 Green LED to indicate value being accepted*
- 4 Key for position adjustment and device reset
- 5 Slot for optional display
- 6 Slot for optional HistoROM[®]/M-DAT

Remote operation

All software parameters are accessible depending on the position of the write protection switch on the device.

Hardware and software for remote operation	HART	PROFIBUS PA	FOUNDATION Fieldbus
FieldCare	v	V	V
FieldXpert SFX100	V	_	V
NI-FBUS Configurator	_	_	V
HistoROM®/M-DAT	v	v	V

FieldCare

FieldCare is an Endress+Hauser asset management tool based on FDT technology. With FieldCare, you can configure all Endress+Hauser devices as well as devices from other manufacturers that support the FDT standard.

FieldCare supports the following functions:

- Configuration of transmitters in offline and online mode
- Loading and saving device data (upload/download)
- HistoROM[®]/M-DAT analysis
- Documentation of the measuring point

Connection options:

- HART via Commubox FXA195 and USB interface of a computer
- PROFIBUS PA via segment coupler and PROFIBUS interface card
- Service interface with Commubox FXA291 and ToF adapter FXA291 (USB).

For further information, please contact your local Endress+Hauser Sales Center.

Field Xpert SFX100

Field Xpert is an industrial PDA with integrated 3.5" touchscreen from Endress+Hauser based on Windows Mobile. It offers wireless communication via the optional VIATOR Bluetooth modem from Endress+Hauser. Field Xpert also works as a stand-alone device for asset management applications. For details, refer to BA00060S/04/EN.

Commubox FXA195

For intrinsically safe HART communication with FieldCare via the USB interface. For details refer to TI00404F/00/EN.

Commubox FXA291

The Commubox FXA291 connects Endress+Hauser field devices with a CDI interface (=Endress +Hauser Common Data Interface) to the USB interface of a personal computer or a notebook. For details refer to TI00405C/07/EN.

For the following Endress+Hauser devices you need the "ToF adapter FXA291" as an additional accessory:

- Cerabar S PMC71, PMP7x
- Deltabar S PMD7x, FMD7x
- Deltapilot S FMB70

ToF Adapter FXA291

The ToF adapter FXA291 connects the Commubox FXA291 with devices of the ToF platform, pressure equipment and Gammapilot via the USB interface of a personal computer or a notebook. For details refer to KA00271F.

Profiboard

For connecting a PC to the PROFIBUS.

Proficard

For connecting a laptop to the PROFIBUS.

FF configuration program

FF configuration program, such as NI-FBUS Configurator, to

- connect devices with "FOUNDATION Fieldbus signal" into an FF-network
- set FF-specific parameters

Operation with NI-FBUS Configurator:

The NI-FBUS Configurator is an easy-to-use graphical environment for creating linkages, loops, and a schedule based on the fieldbus concepts.

You can use the NI-FBUS Configurator to configure a fieldbus network as follows:

- Set block and device tags
- Set device addresses
- Create and edit function block control strategies (function block applications)
- Configure vendor-defined function and transducer blocks
- Create and edit schedules
- Read and write to function block control strategies (function block applications)
- Invoke methods specified in the manufacturer-specific DD (e.g. basic device settings)
- Display DD menus (e.g. tab for calibration data)
- Download a configuration
- Verify a configuration and compare it to a saved configuration
- Monitor a downloaded configuration
- Replace devices
- Save and print a configuration

HistoROM [®] /M-DAT (optional)	HistoROM [®] /M-DAT is a memory module which can be attached to every ele HistoROM [®] /M-DAT can be retrofitted at any stage (order number: 520277	
	 Your benefits Quick and safe commissioning of the same measuring points by copying to one transmitter to another transmitter. Reliable process monitoring thanks to cyclical recording of pressure and s measured values Simple diagnosis by recording diverse events such as alarms, configuration measuring range undershoot and overshoot for pressure and temperature overshoot and undershoot for pressure and temperature etc. Analysis and graphic evaluation of the events and process parameters via scope of supply). 	ensor temperature n changes, counters for e as well as user limit
	You can copy data from one transmitter to another transmitter when operat Fieldbus device via an FF configuration program. You need the Endress+Hat program, the Commubox FXA291 service interface and the ToF adapter FXA the data and events saved in the HistoROM [®] /M-DAT.	user FieldCare operating
	Ordering information:	
	Product Configurator, order code for "Additional options:", version " $\mathbb N$ " or	
	Product Configurator, order code for "Application package:", option "EN" or	
	as a separate accessory (part no.: 52027785).	
	For further information, please contact your local Endress+Hauser Sale	es Center.
System integration	The device can be given a tag name (max. 8 alphanumeric characters).	
	Designation	Option ¹⁾
	Measuring point (TAG), see additional specifications	Z1
	Bus address, see additional spec.	Z2

1) Product Configurator, order code for "Identification"

Planning instructions for diaphragm seal systems

NOTICE

Diaphragm seal systems sized/ordered incorrectly

The performance and the permitted range of application of a diaphragm seal system depend on the process membrane used, the fill fluid, the coupling, the design and on the process and ambient conditions present in the individual application.

• To help you select the right diaphragm seal systems for your particular applications, Endress +Hauser provides its customers with the "Applicator Sizing Diaphragm Seal" selection tool, which is available free of charge at www.endress.com/applicator or as a download.

Home > Pressure	> Product Sizing >	Diaphragm Seal							Help Contac
Sizing	g Diaphragm S	eal					Dimensionin	g pressure devices	
0	Sizing Chart Exter	ded Order Code							
Gene	ral parameters								
Produ	ict ()	Cerabar S PMP75	\sim					1	
TAG					Extended Order Code	PMP75-	1H1183A	1	
								ans	
0	1 Message(s)							~	
Tran	smitter data 🕕				Measurement accuracy and of	ffset 🕕			
			unit				% span /10K 🛛 🗸	mbar/10K 🗸 🗸	
Senso	or 🕕	1bar/100kPa/15psi gauge	\sim		Error due to change in process		0.048	0.477	
Adjus	ited span 🕕	1 000	mbar	\sim	temperature				
Prir	nt Sizing Add	to Cart						Reset	

For further details, or for information on an optimum diaphragm seal solution, your local Endress+Hauser Sales Center is also always happy to help.

Applications

Diaphragm seal systems should be used if the process and the device need to be separated. Diaphragm seal systems offer clear advantages in the following instances:

- In the case of extreme process temperatures
- For aggressive media
- In the case of process media that crystallize
- In the case of corrosive or highly various process media or process media with solids content
- In the case of heterogeneous and fibrous process media
- If extreme measuring point cleaning is necessary, or in the event of very damp mounting locations
- If the measuring point is exposed to severe vibrations
- For mounting locations that are difficult to access

Design and mode of	Diaphragm seals act as separators between the measuring system and the process.
operation	 A diaphragm seal system consists of: A diaphragm seal in a one-sided system, e.g. FMD77 or two diaphragm seals in a two-sided system, e.g. FMD78 One capillary tube or two capillary tubes Fill fluid A differential pressure transmitter
	The process pressure acts via the process membrane of the diaphragm seal on the liquid-filled system, which transfers the process pressure via the capillary tube onto the sensor of the differential pressure transmitter.
	Endress+Hauser delivers all diaphragm seal systems as welded versions. The system is hermetically sealed, which ensures greater reliability.
	 The diaphragm seal determines the application range of the system on the basis of The diameter of the process membrane The stiffness and material of the process membrane The design (oil volume)
	Diameter of the process membrane
	The greater the diameter of the process membrane (less stiff), the smaller the temperature effect on the measurement result.
	Stiffness of the process membrane
	The stiffness depends on the diameter of the process membrane, the material, any existing coating, and the thickness and shape of the process membrane. The thickness of the process membrane and the shape are determined by the design. The stiffness of a process membrane of a diaphragm seal influences the temperature application range and the measured error caused by temperature effects
	The Endress+Hauser TempC Membrane: Highest accuracy and process safety when measuring pressure and differential pressure using diaphragm seals
	 To measure with even greater accuracy in these applications and to increase process safety, Endress +Hauser has developed the TempC Membrane which is based on a completely revolutionary technology. This membrane guarantees the utmost level of accuracy and process safety in diaphragm seal applications. The very low temperature effect minimizes the effect of process and ambient temperature fluctuations, thereby guaranteeing accurate and reliable measurements. Measurement inaccuracies caused by temperature are reduced to a minimum. The TempC Membrane can be used at temperatures between -70 °C (-94 °F) and +400 °C (+752 °F). This guarantees maximum process safety even for very long sterilization and cleaning cycles (SIP/CIP) in tanks and pipes at high temperatures. Smaller instrumentation dimensions are possible thanks to the TempC Membrane. With a smaller process connection, the new membrane measures at least as accurately as a conventional membrane with a larger diameter. Due to the geometry of the membrane, an overshoot occurs initially immediately following a temperature shock. This results in a transient response, the duration and deviation of which are significantly less compared to traditional membrane types. In the case of batch processes, these shorter recovery times mean a far higher level of availability of the production facilities. In the case of TempC Membranes, the effect of the overshoot on the output signal can be reduced by adjusting the damping.
	Ordering information:
	See the Product Configurator for the individual process connection and the choice of process membrane.
	Selection in the Applicator:
	Under "Transmitter data" in the "Membrane material" field.
	Capillary
	Diaphragm seals are used with the following capillary internal diameters as standard:

Diaphragm seals are used with the following capillary internal diameters as standard: • < DN 50: 1 mm (0.04 in) • > DN 50: 2 mm (0.08 in)

The capillary tube influences the thermal change, the ambient temperature operating range and the response time of a diaphragm seal system as a result of its length and internal diameter.

Fill fluid

	The medium and ambient temperatures as well as the process pressure are very important factors to be considered when selecting the fill fluid. Pay attention to the temperatures and pressures during commissioning and cleaning. Another selection criterion is the compatibility of the fill fluid with the requirements of the medium. For example, only fill fluids that do not present a health hazard may be used in the food industry, e.g. vegetable oil or silicone oil (see also the following section "Diaphragm seal fill fluids").	
	The fill fluid used influences the thermal change, the temperature application range of a diaphragm seal system and the response time. A temperature change causes a volume change in the fill fluid. The volume change is dependent on the expansion coefficient and on the volume of the fill fluid at calibration temperature (constant in range: $+21$ to $+33$ °C ($+70$ to $+91$ °F)). The application range can be extended by a fill fluid with a lower expansion coefficient and a shorter capillary.	
	For example, the fill fluid expands in the event of a temperature increase. The additional volume presses against the process membrane of a diaphragm seal. The stiffer a process membrane is, the greater its return force, which counteracts a volume change and acts together with the process pressure on the measuring cell, thus shifting the zero point.	
Differential pressure transmitter	The differential pressure transmitter influences the temperature operating range, the TK zero point and the response time as a result of the volume of its side flange and as a result of its volume change. The volume change is the volume that has to be shifted in order to pass through the complete measuring range.	
	Differential pressure transmitters from Endress+Hauser are optimized with regard to the minimum volume change and side flange.	

Diaphragm seal filling oils

Medium	P _{abs} = 0.05 bar (0.725 psi) ¹⁾	$P_{abs} = \ge 1 \text{ bar (14.5 psi)}^{2}$
Silicone oil	-40 to +180 °C (-40 to +356 °F)	-40 to +250 °C (-40 to +482 °F)
High-temperature oil	-20 to +200 °C (-4 to +392 °F)	-20 to +400 °C (-4 to +752 °F) ^{3) 4) 5)}
Low-temperature oil	-70 to +120 °C (-94 to +248 °F)	-70 to +180 °C (-94 to +356 °F)
Vegetable oil	-10 to +160 °C (+14 to +320 °F)	-10 to +220 °C (+14 to +428 °F)
Inert oil	-40 to +100 °C (-40 to +212 °F)	-40 to +175 °C (-40 to +347 °F) ^{6) 7)}

1) Permitted temperature range at p_{abs} = 0.05 bar (0.725 psi) (observe temperature limits of the device and the system!)

2) Permitted temperature range at $p_{abs} \ge 1$ bar (14.5 psi) (observe temperature limits of the device and the system!)

3) 325 °C (617 °F) at \geq 1 bar (14.5 psi)absolute pressure.

4) 350 °C (662 °F) at \geq 1 bar (14.5 psi) absolute pressure (max. 200 hours).

5) 400 °C (752 °F) at \geq 1 bar (14.5 psi) absolute pressure (max. 10 hours).

6) 150 °C (302 °F) at ≥1 bar (14.5 psi)absolute pressure.

7) 175 °C (347 °F) at \geq 1 bar (14.5 psi) absolute pressure (max. 200 hours).

The calculation of the operating temperature range of a diaphragm seal system depends on the fill fluid, capillary length and capillary internal diameter, process temperature and oil volume of the diaphragm seal. Detailed calculations, e.g. for temperature ranges, vacuum pressure ranges and temperature ranges, are done separately in the Applicator "Sizing Diaphragm Seal".




Operating temperature range

The operating temperature range of a diaphragm seal system depends on the fill fluid, capillary length and internal diameter, process temperature and oil volume of the diaphragm seal.

The range of application can be extended by using a fill fluid with a smaller expansion coefficient and a shorter capillary.

Response time	The viscosity of the filling oil, the capillary length and the capillary internal diameter influence the frictional resistance. The greater the frictional resistance, the longer the response time. Furthermore, the volume change of the measuring cell influences the response time. The lower the volume change of the measuring cell, the less filling oil has to be shifted in the diaphragm seal system.				
	To help you select the right diaphragm seal systems for your particular applications, Endress+Hauser provides its customers with the "Applicator Sizing Diaphragm Seal" selection tool, which is available free of charge at "www.endress.com/applicator" or can be ordered on a DVD.				
Cleaning instructions	Endress+Hauser offers flushing rings as accessories to clean process isolating diaphragms without taking the transmitters out of the process.				
	For further information please contact your local Endress+Hauser Sales Center.				
	We recommend you perform CIP (cleaning in place (hot water)) before SIP (sterilization in place (steam)) for pipe diaphragm seals. The frequent use of sterilization in place (SIP) will increase the stress on the process isolating diaphragm. Under unfavorable circumstances, frequent temperature changes can lead - on the long term - to material fatigue of the process isolating diaphragm and possibly to a leakage.				
Installation instructions	 Diaphragm seal systems A diaphragm seal together with the transmitter form a closed, calibrated system, which has been filled through openings in the diaphragm seal and in the transmitter's measurement system. These openings are sealed and must not be opened. In the case of devices with diaphragm seals and capillaries, the zero point shift caused by the hydrostatic pressure of the filling liquid column in the capillaries must be taken into account when selecting the measuring cell. If a measuring cell with a small measuring range is selected, the sensor nominal range can be overdriven as a result of position adjustment (see the figure and the example below). For devices with a capillary a suitable fastening device (mounting bracket) is recommended. When mounting, sufficient strain relief must be provided for the capillary line to prevent the capillary from bending (capillary bending radius ≥ 100 mm (3.94 in)). For more detailed installation instructions, Endress+Hauser provides its customers with the free "Applicator Sizing Diaphragm Seal" selection tool, which is available online at "www.endress.com/ applicator" or as a download. 				
	p_{i} $\nabla \max.$ $AH = 1 m (3.3 ft)$ $W = 1.8 m (5.9 ft)$ $Hv = 1.8 m (5.9 ft)$				



- Capillary with silicone oil: $\rho_{FI} = 0.96 \text{ kg} (2.12 \text{ lb}) \text{ dm}^3$ Vessel with water: $\rho_M = 1.0 \text{ kg} (2.21 \text{ lb}) \text{ dm}^3$ 1
- 2

Pressure on the negative side of the differential pressure transmitter (p-) when the vessel is empty (minimum level):

$$p_{-} = p_{HV} + p_{H1} = Hv \cdot \rho_{FI} \cdot g + H1 \cdot \rho_{FI} \cdot g + p_{i}$$

= 1,8 m \cdot 0,96 $\frac{kg}{dm^{3}} \cdot 9,81 \frac{m}{s^{2}} + 0,3 m \cdot 0,96 \frac{kg}{dm^{3}} \cdot 9,81 \frac{m}{s^{2}} + p_{i}$
= 197,77 mbar + p_i

Pressure on the positive side of the differential pressure transmitter (p+) when the vessel is empty (minimum level):

$$p_{+} = p_{HU} + p_{H1} = Hu \cdot \rho_{M} \cdot g + H1 \cdot \rho_{FI} \cdot g + p_{i}$$

= 0.2 m \cdot 1 \frac{kg}{dm^{3}} \cdot 9.81 \frac{m}{s^{2}} + 0.3 m \cdot 0.96 \frac{kg}{dm^{3}} \cdot 9.81 \frac{m}{s^{2}} + p_{i}
= 47.87 mbar + p_{i}

Differential pressure at the transmitter ($\Delta p_{transmitter}$) when the vessel is empty:

 $\Delta p_{\text{Transmitter}} = p_{+} - p_{-}$ = 47,87 mbar - 197,77 mbar = - 149,9 mbar

Result:

When the vessel is full, a differential pressure of -51.80 mbar (-0.762 psi) would be present at the differential pressure transmitter. When the vessel is empty, a differential pressure of -149.90 mbar (-2.2485 psi) is present. A 500 mbar (7.5 psi) measuring cell is therefore necessary for this application.

Capillary

In order to obtain more precise measurement results and to avoid a defect in the device, mount the capillaries as follows:


- Vibration-free (in order to avoid additional pressure fluctuations)
- Not in the vicinity of heating or cooling lines
- Insulate the capillaries if the ambient temperature is below or above the reference temperature
- With a bending radius \geq 100 mm (3.94 in)
- When using diaphragm seal systems with a capillary, sufficient strain relief must be provided to
 prevent the capillary from bending (capillary bending radius ≥ 100 mm (3.94 in)).
- In the case of devices with diaphragm seals and capillaries, the zero point shift caused by the hydrostatic pressure of the filling liquid column in the capillaries must be taken into account when selecting the measuring cell. If a measuring cell with a small measuring range is selected, a position adjustment can cause range violation.

A0023962

A002398:

Heat insulation - FMD77


The FMD77 must only be insulated up to a certain height. The maximum permitted insulation height applies to an insulation material with a heat conductivity $\leq 0.04 \text{ W/(m x K)}$ and to the maximum permitted ambient and process temperature. The data were determined under the most critical application "quiescent air".



1 Insulation material

- A Transmitter horizontal, temperature isolator long
- *B* Transmitter vertical, temperature isolator long
- C Transmitter horizontal, temperature isolator short
- D Transmitter vertical, temperature isolator short

Without insulation, the ambient temperature decreases by 5 K.



1 Insulation material

Item	Design	Ambient temperature T _A	Process temperature T _P	Option ¹⁾
E	U-bracket, transmitter horizontal (for devices which require a CRN approval)		Max. 350 °C (662 °F) dependent on the diaphragm seal fill fluid used	2)

Product Configurator, order code for "Process connection" In combination with CSA approval. 1)


2)

Vacuum applications


Mounting instructions

For applications under vacuum, Endress+Hauser recommends mounting the pressure transmitter below the lower diaphragm seal. This prevents a vacuum load of the diaphragm seal caused by the presence of filling oil in the capillaries.

When the pressure transmitter is mounted above the lower diaphragm seal, the maximum height difference H1, in accordance with the following illustrations, must not be exceeded:



The maximum height difference is dependent on the density of the filling oil and the lowest pressure that is ever allowed to occur at the diaphragm seal on the positive side (empty vessel), see the following illustration:



- A Height difference H1
- *B Pressure at diaphragm seal*
- 1 Low-temperature oil
- 2 Vegetable oil
- 3 Silicone oil
- 4 High-temperature oil
- 5 Inert oil

Certificates and approvals

CE mark	The device meets the legal requirements of the relevant EC directives. Endress+Hauser confirms that the device has been successfully tested by applying the CE mark.
RCM-Tick marking	The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products bear the RCM-Tick marking on the nameplate.
	A0029563
Ex approvals	 ATEX FM CSA NEPSI IECEx GOST on request Also combinations of different approvals
	All explosion protection data are given in separate documentation which is available upon request. The Ex documentation is supplied as standard with all Ex-devices $\rightarrow \cong 119$.
EAC conformity	The measuring system meets the legal requirements of the applicable EAC guidelines. These are listed in the corresponding EAC Declaration of Conformity along with the standards applied.
	Endress+Hauser confirms successful testing of the device by affixing to it the EAC mark.
Suitable for hygiene	For information on installation and approvals, see documentation SD02503F "Hygiene approvals".
applications	For information on 3-A and EHEDG-tested adapters, see documentation TI00426F "Weld-in adapter, process adapter and flanges".
Certificate of current Good	Product Configurator, order code for "Test, Certificate" option "JG"
Manufacturing Practices (cGMP)	 The certificate is only available in English
	Materials of construction of product wetted partsTSE compliance
	 Polishing and surface finish Material/ compound compliance table (USP Class VI, FDA conformity)
Functional safety SIL/ IEC 61508 Declaration of Conformity (optional)	The Deltabar S with 4 to 20 mA output signal has been developed in accordance with the IEC 61508 standard. The device can be used for flow, level and differential pressure monitoring up to SIL 3. For a detailed description of the safety functions with the Deltabar S, settings and functional safety data, see the "Functional safety manual - Deltabar S" SD00189P.
	For devices up to SIL 3 / IEC 61508 Declarations of Conformity see:
	Ordering information:
	Product Configurator, order code for "Additional options 1", version "E"
Overfill prevention	WHG (see document ZE00259P/00/EN)
	Ordering information:
	Product Configurator, order code for "Approval", option "6".
CRN approval	PMD75
	A CRN approval is available for some device versions. These devices are fitted with a separate plate bearing the registration number CRN 0F20813.5C. A CRN-approved process connection can be obtained in one of the following ways:

	 CRN-approved process connection must be ordered with a CSA approval CRN-approved process connection must be ordered with the "CRN" option in the order code for "Additional approval".
	FMD77, FMD78
	A CRN approval is available for some device versions. A CRN-approved process connection with a CSA approval must be ordered for a CRN-approved device. These devices are fitted with a separate plate bearing the registration number CRN 0F10524.5C.
	Ordering information:
	Product Configurator, order code for "Process connection; material" and
	Product Configurator, order code for "Approval" (only in conjunction with an approved process connection)
Other standards and guidelines	The applicable European guidelines and standards can be found in the relevant EU Declarations of Conformity. The following standards were also applied:
	IEC 62828-1 / DIN EN 60770 and IEC 62828-2 / DIN EN 60770:
	Transmitters for use in industrial-process control systems. Part 1: Methods for inspection and routine testing
	DIN 16086:
	Electrical pressure measuring instruments, pressure sensors, pressure transmitters, pressure measuring instruments, concepts, specifications on data sheets
	EN 61326-X:
	EMC product family standard for electrical equipment for measurement, control and laboratory use.
	EN 60529:
	Degrees of protection provided by enclosures (IP code)
Pressure Equipment	Pressure equipment with allowable pressure \leq 200 bar (2900 psi)
Directive 2014/68/EU (PED)	Pressure equipment (with a maximum allowable pressure PS \leq 200 bar (2 900 psi)) can be classified as pressure accessories in accordance with Pressure Equipment Directive 2014/68/EU. If the maximum allowable pressure is \leq 200 bar (2 900 psi) and the pressurized volume of the pressure equipment is \leq 0.1 l, the pressure equipment is subject to the Pressure Equipment Directive (cf. Pressure Equipment Directive 2014/68/EU, Article 4, point 3). The Pressure Equipment Directive only requires that the pressure equipment shall be designed and manufactured in accordance with the "sound engineering practice of a Member State".
	Reasons:
	 Pressure Equipment Directive (PED) 2014/68/EU Article 4, point 3 Pressure Equipment Directive 2014/68/EU, Commission's Working Group "Pressure", Guideline A-05 + A-06
	Note:
	A partial examination shall be performed for pressure instruments that are part of safety equipment for the protection of a pipe or vessel from exceeding allowable limits (safety accessory in accordance with Pressure Equipment Directive 2014/68/EU, Article 2, point 4).
	Pressure equipment with allowable pressure > 200 bar (2 900 psi)
	Pressure equipment designated for application in every process fluid having a pressurized volume of <0.1 l and a max. allowable pressure PS > 200 bar (2 900 psi) must satisfy the essential safety requirements set out in Annex I of the Pressure Equipment Directive 2014/68/EU. According to Article 13 pressure equipment shall be classified by category in accordance with Annex II. Taking into account the low pressurized volume discussed above, the pressure devices are classed as category I pressure equipment. These devices must then bear the CE marking.

	Reasons:							
	 Pressure Equipment Directive 2014/68/EU, Article 13, Annex II Pressure Equipment Directive 2014/68/EU, Commission's Working Group "Pressure", Guideline A-05 							
	Note:							
	for the protec	mination shall be perfo ction of a pipe or vessel e Equipment Directive 2	from exceeding allow	wable lim	its (safet			
	The following	also applies:						
	Suitable for PMD75, PN	th pipe diaphragm seal r stable gases in group V 420 r stable gases in group	1, category II, module					
Manufacturer declarations Depending on the desired configuration, the following documents can be the device: • FDA conformity • TSE-free: materials free from animal origin • Regulation (EC) No. 2023/2006 (GMP) • Regulation (EC) No. 1935/2004 on materials and articles intended to Downloading the Declaration of Conformity www.endress.com → Download							-	
Marine approval	 GL: FMD78 	3 PMD75						
marine approval	 ABS: FMD7 							
	Ordering information:							
	Product Conf	igurator, order code for	"Additional options	1" or "Add	litional oj	ptions 2",	version "	S".
Classification of process sealing between electrical systems and (flammable or combustible) process fluids in accordance with ANSI/ISA 12.27.01	waive the use required by th instruments of saving install	ser devices are designed of - and save the cost ne process sealing secti comply with the North- ation for pressurized a seal class assigned (sin	of installing - externa ons of ANSI/NFPA 7 American installation oplications with haza	al second 0 (NEC) a n practice rdous flu	ary proce and CSA 2 e and pro	ess seals i 22.1 (CEC vide a vei	n the cor C). These ry safe ar	nduit as nd cost-
	Device	Approval		Single se	eal MWP			
	PMD75	CSA C/US IS, XP		420 bar	(6 300 psi			
	FMD77	CSA C/US IS, XP		160 bar	(2 400 psi			
	FMD78	CSA C/US IS, XP		160 bar	(2 400 psi)		
	Further infor	mation can be found in	the control drawing	s of the r	elevant d	evices.		
Inspection certificate								
Designation					FMD77	FMD78	PMD75	Option
3.1 Material documentation, wetter	d metal parts, EN	10204-3.1 inspection cer	tificate		~	~	v	B ¹⁾⁴⁾
Conformity to NACE MR0175, wet	formity to NACE MR0175, wetted metallic parts \checkmark \checkmark \checkmark $C^{1)4)}$						C ^{1) 4)}	

Individual test, test report

Pressure test, internal procedure, test report

EN10204-3.1 material, NACE MR0175, wetted metal parts, inspection certificate

EN10204-3.1 material wetted parts +Ra, Ra= surface roughness, dimensional check, inspection certificate

D ^{1) 4)}

3 1) 2)

4¹⁾²⁾

6 1) 2)

V

r

V

_

V

V

v

v

V

r

r

_

Designation	FMD77	FMD78	PMD75	Option
Delta-Ferrite measurement, internal procedure, wetted metallic parts, inspection certificate	_	V	_	8 ¹⁾²⁾
3.1 Material documentation, wetted metal parts, EN10204-3.1 inspection certificate	V	~	v	JA ^{3) 4)}
Conformity to NACE MR0175, wetted metallic parts	V	~	v	JB ^{3) 4)}
Conformity to NACE MR0103, wetted metallic parts	V	V	v	JE ^{3) 4)}
Helium leak test, internal procedure, inspection certificate	v	V	v	KD ³⁾
Pressure test, internal procedure, inspection certificate	v	~	v	KE 3)
PMI test (XRF), internal procedure, metal parts in contact with the medium	V	~	v	KG ³⁾
Welding documentation, wetted/pressurized seams	—	V	_	KS

Product Configurator, order code for "Additional options 1" Product Configurator, order code for "Additional options 2" 1)

2) 3) Product Configurator, order code for "Test, Certificate"

The choice of this feature for coated process isolating diaphragms/process connections refers to the metal base material. 4)

Calibration

Designation	FMD77	FMD78	PMD75	Option ¹⁾
Nominal range; mbar/bar	r	~	r	1
Nominal range; kPa/MPa	r	r	r	2
Nominal range; mmH2O/mH2O	r	V	r	3
Nominal range; inH2O/ftH2O	r	V	r	4
Nominal range; psi	v	V	v	6
Factory calibration certificate, 5-point; see additional specification	v	V	v	С
DKD/DAkkS certificate; see additional specification	r	V	r	D
Customized pressure; see additional specification	r	V	r	Е
Customized level; see additional specification	v	V	v	F
Customized flow; see additional specification	_	-	v	G
Customized pressure + 5-point factory calibration certificate; see additional specification	v	V	v	Н
Customized level + 5-point factory calibration certificate; see additional specification	r	V	r	Ι
Customized flow + 5-point factory calibration certificate; see additional specification	r	V	r	J
Platinum; see additional specification	-	-	v	К
Platinum + factory calibration certificate 5-point; see additional specification	_	-	r	L
Platinum + DKD/DAkkS certificate; see additional specification	_	-	r	М

1) Product Configurator, order code for "Calibration; unit"

Service

Designation	Option ¹⁾
Cleaned of oil+grease ²⁾	НА
Cleaned for oxygen service ²⁾	HB
Cleaned of PWIS (paint-wetting impairment substances) ²⁾	НС

1) Product Configurator, order code for "Service"

2) Device only, not accessories or enclosed accessories.

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
 -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
 Open product page -> The "Configure" button to the right of the product image opens the Product
 Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com
 - Product Configurator the tool for individual product configuration
- Up-to-the-minute configuration data
 - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
 - Automatic verification of exclusion criteria
 - Automatic creation of the order code and its breakdown in PDF or Excel output format
 - Ability to order directly in the Endress+Hauser Online Shop

Special device versionsEndress+Hauser offers special device versions as Technical Special Products (TSP).For further information please contact your local Endress+Hauser Sales Center.

Scope of delivery • Measuring device

- Optional accessories
 Drive On constitute In structure time
- Brief Operating Instructions
- Calibration certificates
- Optional certificates

Measuring point (TAG)	Order code	895: Marking
	Option	Z1: Tagging (TAG), see additional spec.
	Position of the measuring point marking	To be selected in the additional specifications: Tag plate Stainless Steel Self-adhesive paper label Supplied label/plate RFID TAG RFID TAG + Tag plate Stainless Steel RFID TAG + Self-adhesive paper label RFID TAG + Supplied label/plate
	Definition of the measuring point designation	To be defined in the additional specifications: 3 lines containing up to 18 characters each The measuring point designation appears on the selected label and/or the RFID TAG.
	Identification on electronic nameplate (ENP)	32 characters

Configuration data sheet

Pressure

The following configuration data sheet must be completed and included with the order if the option "E" or "H" has been selected in the Product Configurator, order code for "Calibration; Unit".

Pressure unit				
□ mbar □ bar □ psi	$\begin{array}{ccc} & mmH_2O & {}^{1)} \\ \hline & mH_2O & {}^{1)} \\ \hline & ftH_2O & {}^{1)} \\ \hline & inH_2O & {}^{1)} \end{array}$	$\begin{array}{c c} mmHg ^{2)} \\ \hline nHg ^{2)} \\ gf/cm^{2} \\ \hline kgf/cm^{2} \end{array}$	 Pascals hPa kPa MPa 	 torr g/cm² kg/cm² lb/ft² atm

1) The conversion factor for the pressure unit is based on a reference temperature of 4 °C (39.2 °F).

2) The conversion factor of the pressure unit refers to a reference temperature of 0 $^{\circ}$ C (32 $^{\circ}$ F).

[Pressure engineering unit] [Pressure engineering unit]


Display
 Display of the content of the main line (option depends on sensor and communication variant) Primary value [PV] (default) Main Value [%] Pressure Current [mA] (HART only) Temperature Error number Alternating display

Damping		
Damping:	 sec (Default 2 sec)	

Smallest calibratable span (preset at factory) \rightarrow 🗎 12

Level

The following configuration data sheet must be completed and included with the order if the option "F" or "T" has been selected in the Product Configurator, order code for "Calibration; Unit".



1) The conversion factor for the pressure unit is based on a reference temperature of 4 $^{\circ}C$ (39.2 $^{\circ}F$).

2) The conversion factor of the pressure unit refers to a reference temperature of 0 °C (32 °F).

Display

Display of the content of the main line (option depends on sensor and communication variant)

- □ Primary value [PV] (default)
- □ Main Value [%]
- □ Pressure
- □ Current [mA] (HART only)
- □ Temperature
- Level before Lin.
- Tank content
- Error number
- Alternating display

Damping

Damping:

sec (Default 2 sec)

Flow

The following configuration data sheet must be completed and included with the order if the option "G" or "J" has been selected in the Product Configurator, order code for "Calibration; Unit".

Pressure unit	Flow Unit / Measured Value (PV)
	Mass Volume Volume Volume
	Operation Norm Standard Conditions Conditions Conditions
$\left[\begin{array}{cccccccccccccccccccccccccccccccccccc$	$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$

1) The conversion factor for the pressure unit is based on a reference temperature of 4 $^{\circ}C$ (39.2 $^{\circ}F$).

2) The conversion factor of the pressure unit refers to a reference temperature of 0 °C (32 °F).

3) Term used in device and operating software. bbl = US Barrel (oil)

4) Order designation

Out	tput Characteristic				
	linear (HART only) Operation Point		square root (HART only) Operation Point		
	Maximum pressure	 [Pressure engineering unit] 	Maximum pressure		[Pressure engineering unit]
	Max Flow	_ [flow unit]	Max Flow		[flow unit]
	LRV	_ [Pressure engineering unit]	LRV		[Pressure engineering unit]
	(Lower Range Value (HART only))		(Lower Range Value (HAI	RT only))	

Low flow cut off

Value:

[%] (default = 5%)

Display

Display of the content of the main line (option depends on sensor and communication variant)

□ Flow

□ Totalizer 1

Totalizer 2

- □ Primary value [PV] (default)
- Main Value [%]
- Pressure
- Current [mA] (HART only) Temperature

□ Error number □ Alternating display

Damping		
Damping:	 sec (Default 2 sec)	

HistoROM [®] /M-DAT	The HistoROM®/M-DA	T is a memory module that can be attached to any electronic insert.			
	Ordering information: Product Configurator, order code for "Additional options 1" or Additional options 2", version "N" or				
	(part no.: 52027785).				
Welding flanges and weld-in adapters					
Manifolds	See the $\rightarrow \blacksquare 52$.	52.			
	For further details, see	SD01553P/00/EN "Mechanical accessories for pressure measuring devices".			
Additional mechanical accessories	Oval flange adapters, pressure gauge valves, shutoff valves, siphons, condensate pots, cable shortening kits, test adapters, mounting brackets, flushing rings, block&bleed valves and protective roofs.				
	For details see SD01553P/00/EN "Mechanical accessories for pressure measuring devices".				
Service-specific accessories	Accessories	Description			
	DeviceCare SFE100	Configuration tool for HART, PROFIBUS and FOUNDATION Fieldbus field devices			
		Technical Information TI01134S			
		DeviceCare is available for download at www.software-products.endress.com. You need to register in the Endress+Hauser software portal to download the application.			
	FieldCare SFE500	FDT-based plant asset management tool FieldCare can configure all smart field units in your plant and helps you manage them. By using the status information, FieldCare is also a simple but effective way of checking the status and condition of the field devices.			
		Technical Information TI00028S			
	Field Xpert SMT70, SMT77	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous (Ex Zone 2) and non-hazardous areas. It is suitable for commissioning and maintenance staff. It manages Endress+Hauser and third-party field instruments with a digital communication interface and documents the progress of the work. The SMT70 is designed as a complete solution. It comes with a pre-installed driver library and is an easy-to-use, touch- enabled tool for managing field devices throughout their entire life cycle. The Field Xpert SMT77 for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1. It is suitable for commissioning and maintenance staff for easy management of field instruments with a digital communication interface. The touch-enabled tablet PC is designed as a complete solution. It comes with comprehensive pre-installed driver libraries and offers users a modern software user interface to manage field instruments throughout the entire life cycle.			

Accessories

Field of Activities	Pressure measurement, pow flow:	erful instruments for process pressure, di	fferential pressure,	level and			
	FA00004P/00/EN						
Technical Information	Deltabar S: TI00382P/00/EN	1					
	 EMC test procedures: TI00 Weld-in adapter, adapter a 	241F/00/EN and flanges: TI00426F/00/EN					
Special Documentation	Mechanical accessories for pressure measuring devices: SD01553P/00/EN						
Operating Instructions	4 to 20 mA HART: • Deltabar S: BA00270P/00 • Description of Device Func	9/00/EN Functions Cerabar S/Deltabar S/Deltapilot S: BA00274P/00/EN					
	 PROFIBUS PA: Deltabar S: BA00294P/00/EN Description of Device Functions CerabarS/Deltabar S/Deltapilot S: BA00296P/00/EN 						
	FOUNDATION Fieldbus: • Deltabar S: BA00301P/00/EN • Description of Device Functions Cerabar S/Deltabar S/Deltapilot S: BA00303P/00/EN						
Brief Operating Instructions	f Operating Instructions 4 to 20 mA HART, Deltabar S: KA01018P/00/EN PROFIBUS PA, Deltabar S: KA01021P/00/EN FOUNDATION Fieldbus, Deltabar S: KA01024P/00/EN 						
Functional safety manual (SIL)	Deltabar S (4 to 20 mA): SDO	00189P/00/EN					
Overfill prevention	WHG: ZE00259P/00/DE						
Safety Instructions (XA)	Depending on the approval, t are an integral part of the Op	the following Safety Instructions (XA) are perating Instructions.	e supplied with the	device. They			
Directive		Electronic insert	Documentation	Option ¹⁾			
ATEX II 1/2G Ex ia IIC T6 Ga/Gb (\	WHG)	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00235P	1 (6)			
ATEX II 1/2D Ex ta/tb IIIC Da/Db		4 to 20 mA HART	XA00237P	2			
		PROFIBUS PA, FOUNDATION Fieldbus	XA00280P				
ATEX II 1/3D Ex ta IIIC Da/Dc		4 to 20 mA HART	XA00239P	4			
		PROFIBUS PA, FOUNDATION Fieldbus	XA00282P	_			
ATEX II 2 G Ex d IIC T6 Gb	ATEX II 2 G Ex d IIC T6 Gb		XA00240P	5			
ATEX II 3 G Ex nA II T6 ATEX II 1/2G Ex ia IIC T6 Ga/Gb + ATEX II 1/2D Ex ia IIIC Da/Db ATEX II 1G Ex ia + II 1D Ex iaD		4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00241P	7			
		4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00243P	3			
		4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00275P	8			
ATEX II 1/2G Ex ia IIC T6+II 2G Ex d IIC T6		4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00242P	В			
ATEX II Ex ia/Ex d + FM/CSA IS + . ATEX II 1/2G Ex ia IIC T6+ ATEX II 2G Ex d IIC T6+FM/CSA IS XP Cl.I.II Div.1 Gr.A-G/B-GFM/CSA	;+	4 to 20 mA HART	XA00242P ZD00153P XA01196P	F			

Supplementary documentation

Directive	Electronic insert	Documentation	Option ¹⁾
	PROFIBUS PA, FOUNDATION Fieldbus	XA00242P XA01198P ZD00191P	
IECEx Ex ia IIC T6 Ga/Gb	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XB00004P	Ι
IEC Ex d IIC T6 Gb	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00512P	М
NEPSI Ex ia IIC T6	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00550P	Н
NEPSI Ex d IIC T6	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA00552P	G

1) Product Configurator, order code for "Approval"

Directive	Electronic insert	Documentation	Option ¹⁾
INMETRO Ex ia IIC T6 Ga/Gb	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01318P	J
INMETRO Ex d IIC T6 Gb	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01281P	0
INMETRO Ex ta IIIC Da/Db	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01316P	Z

1) Product Configurator, order code for "Approval"

Installation/Control

Directive	Electronic insert	Documentation	Option ¹⁾	
FM IS Cl.I,II,III Div.1 Gr.A-G,	4 to 20 mA HART	XA01058P	S	
NI Cl.I Div.2 Gr.A-D, AEx ia, Zone 0,1,2,20,21,22	PROFIBUS PA, FOUNDATION Fieldbus	XA01060P		
FM/CSA IS + XP Cl.I Div.1 Gr.A-D, FM/CSA: Zone 1,2	4 to 20 mA HART	XA00591P XA01196P	Q	
	PROFIBUS PA, FOUNDATION Fieldbus	XA00590P XA01198P		
FM DIP Cl.II,III Div.1 Gr.E-G, Zone 21,22	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	FM3017778	Q	
CSA C/US IS Cl.I,II,III Div.1 Gr.A-G,	4 to 20 mA HART	ZD00142P	U	
Cl.I Div.2 Gr.A-D, Ex ia, C: Zone 0,1,2/ US: Zone 0,1,2,20,21,22	PROFIBUS PA, FOUNDATION Fieldbus	ZD00189P		
FM IS + XP Cl.I Div.1 Gr.A-D, Zone 1,2	4 to 20 mA HART	XA01196P	С	
	PROFIBUS PA, FOUNDATION Fieldbus	XA01198P		
FM NI Cl.I Div.2 Gr.A-D, Zone 2	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01064P	R	
FM XP Cl.I Div.1 Gr.A-D, AEx d, Zone 1,2	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	XA01071P	Т	
CSA C/US IS + XP Cl.I Div.1 Gr.A-D, Zone 1,2	4 to 20 mA HART	ZD00153P	D	
	PROFIBUS PA, FOUNDATION Fieldbus	ZD00191P		
ATEX II Ex ia/Ex d + FM/CSA IS + XP ATEX II 1/2G Ex ia IIC T6+ ATEX II 2G Ex d IIC T6+FM/CSA IS + XP	4 to 20 mA HART	XA00242P ZD00153P XA01196P	F	
Cl.I.II Div.1 Gr.A-G/B-GFM/CSA: Zone 1,2	PROFIBUS PA, FOUNDATION Fieldbus	XA00242P XA01198P ZD00191P		
CSA C/US XP Cl.I Div.1 Gr.B-D, Ex d, Zone 1,2	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	ZD00229P	V	
CSA C/US Cl.II, III Div.1 Gr.E-G	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	CSA1509834	W	
CSA C/US General Purpose	4 to 20 mA HART, PROFIBUS PA, FOUNDATION Fieldbus	-	Z	

1) Product Configurator, order code for "Approval"



www.addresses.endress.com

