

Technical Information

iTHERM ModuLine TM151

Innovative, highly modular and robust RTD or TC thermometer for a wide range of industrial applications

Complete with barstock thermowell or to be used with onsite thermowell



Application

- For universal use
- Measuring range: -200 to $+1\,100$ °C (-328 to $+2\,012$ °F)
- Pressure range up to 500 bar (7 252 psi)
- Vibration-resistant sensor elements up to 60g
- Improved ease of maintenance (sensor replacement without process shutdown), easy and safe recalibration of the measuring point

Head transmitters

All Endress+Hauser transmitters are available with enhanced measurement accuracy and reliability compared to directly wired sensors. Easily customized to the measuring task by choosing the outputs and communication protocols:

- Analog output 4 to 20 mA, HART®
HART® SIL transmitter, optional
- PROFIBUS® PA, FOUNDATION Fieldbus™, PROFINET over Ethernet-APL; IO-Link®

Your benefits

- Second process seal with failure indication offering valuable device health status information
- iTHERM QuickSens: fastest response times of 1.5 s for optimum process control
- iTHERM StrongSens: unsurpassed vibration resistance ($\leq 60g$) for ultimate plant safety
- iTHERM QuickNeck – cost and time savings thanks to simple, tool-free recalibration
- Bluetooth® connectivity (optional)
- International certification: explosion protection according to ATEX, IECEx, CSA C/US and CCC

Table of contents






Function and system design	3	Pre-defined versions	61
iTHERM ModuLine	3	Certificates and approvals	65
Measuring principle	4	Test on thermowell	65
Measuring system	4	Ordering information	66
Modular design	6	Accessories	66
Input	9	Service-specific accessories	66
Measured variable	9	Supplementary documentation	67
Measuring range	9		
Output	9		
Output signal	9		
Family of temperature transmitters	9		
Power supply	10		
Terminal assignment	10		
Terminals	15		
Cable entries	15		
Surge arrester	20		
Performance characteristics	20		
Reference conditions	20		
Maximum measurement error	21		
Influence of ambient temperature	21		
Self-heating	22		
Calibration	22		
Insulation resistance	23		
Installation	23		
Orientation	23		
Installation instructions	23		
Ambient conditions	24		
Ambient temperature range	24		
Storage temperature	24		
Humidity	24		
Climate class	24		
Degree of protection	24		
Shock and vibration resistance	24		
Electromagnetic compatibility (EMC)	24		
Process	24		
Process temperature range	24		
Process pressure range	25		
Mechanical construction	25		
Design, dimensions	25		
Weight	34		
Materials	34		
Thermowell/thermometer connections	36		
Process connections	38		
Geometry of parts in contact with medium	48		
Inserts	48		
Surface roughness	49		
Terminal heads	49		
Extension neck	57		

Function and system design

iTHERM ModuLine

This thermometer is part of the product line of modular thermometers for industrial applications.

Differentiating factors when selecting a suitable thermometer:

Thermowell	Direct contact - without thermowell		Thermowell, welded		Thermowell from barstock material
Device type	Metric				
Thermometer	<p>TM101</p>  <p>A0039102</p>	<p>TM111</p>  <p>A0038281</p>	<p>TM121</p>  <p>A0038194</p>	<p>TM131</p>  <p>A0038195</p>	<p>TM151</p>  <p>A0052360</p>
FLEX segment	F	E	F	E	E
Properties	Excellent price-performance ratio	iTHERM StrongSens and QuickSens inserts	Excellent price-performance ratio with thermowell	<ul style="list-style-type: none"> ▪ iTHERM StrongSens and QuickSens inserts ▪ QuickNeck ▪ Fast response times ▪ Dual-seal technology ▪ Dual-compartment housing 	<ul style="list-style-type: none"> ▪ iTHERM StrongSens and QuickSens inserts ▪ QuickNeck ▪ TwistWell ▪ Fast response times ▪ Dual-seal technology ▪ Dual-compartment housing
Hazardous area	-	EX	-	EX	EX

Measuring principle**Resistance thermometers (RTD)**

These resistance thermometers use a Pt100 temperature sensor according to IEC 60751. The temperature sensor is a temperature-sensitive platinum resistor with a resistance of 100 Ω at 0 °C (32 °F) and a temperature coefficient $\alpha = 0.003851 \text{ } ^\circ\text{C}^{-1}$.

There are generally two different kinds of platinum resistance thermometers:

- **Wire-wound (WW):Wire Wound, WW** In these thermometers, a double coil of fine, high-purity platinum wire is accommodated in a ceramic support. This support is then sealed top and bottom with a ceramic protective layer. Such resistance thermometers not only facilitate very reproducible measurements but also offer good long-term stability of the resistance/temperature characteristic within temperature ranges up to 600 °C (1 112 °F). This type of sensor is relatively large in size and is comparatively sensitive to vibrations.
- **Thin-film platinum resistance thermometers (Thin Film, TF):** A very thin, ultrapure platinum layer, approx. 1 μm thick, is vaporized in a vacuum on a ceramic substrate and then structured photolithographically. The platinum conductor paths formed in this way create the measuring resistance. Additional covering and passivation layers are applied and reliably protect the thin platinum layer from contamination and oxidation, even at high temperatures.

The primary advantages of thin film temperature sensors over wire wound versions are their smaller sizes and better vibration resistance. A relatively low principle-based deviation of the resistance/temperature characteristic from the standard characteristic of IEC 60751 can frequently be observed among TF sensors at high temperatures. As a result, the tight limit values of tolerance class A as per IEC 60751 can only be observed with TF sensors at temperatures up to approx. 300 °C (572 °F).

Thermocouples (TC)

Thermocouples are comparatively simple, robust temperature sensors which use the Seebeck effect for temperature measurement: if two electrical conductors made of different materials are connected at a point, a weak electrical voltage can be measured between the two open conductor ends if the conductors are subjected to a thermal gradient. This voltage is called thermoelectric voltage or electromotive force (emf). Its magnitude depends on the type of conducting materials and the temperature difference between the "measuring point" (the junction of the two conductors) and the "cold junction" (the open conductor ends). Accordingly, thermocouples primarily only measure differences in temperature. The absolute temperature at the measuring point can be determined from these if the associated temperature at the cold junction is known or is measured separately and compensated for. The material combinations and associated thermoelectric voltage/temperature characteristics of the most common types of thermocouple are standardized in the IEC 60584 and ASTM E230/ANSI MC96.1 standards.


Measuring system

Endress+Hauser offers a complete portfolio of optimized components for the temperature measuring point – everything you need for the seamless integration of the measuring point into the overall facility. These include:

- Power supply unit/barrier
- Display units
- Surge arrester



For more information, see the brochure "System Components - Solutions for a Complete Measuring Point" (FA00016K)




A0035235

1 Example of application, measuring point layout with additional Endress+Hauser components

- 1 Installed iTHERM thermometer with HART® communication protocol
- 2 RIA15 loop-powered process indicator - The process indicator is incorporated into the current loop and displays the measuring signal or the HART® process variables in digital form. The process display unit does not require an external power supply. It is powered directly from the current loop.
- 3 Active barrier RN42 - The RN42 (17.5 V_{DC}, 20 mA) active barrier has a galvanically isolated output for supplying voltage to loop-powered transmitters. The universal power supply works with an input supply voltage of 24 to 230 V AC/DC, 0/50/60 Hz, which means that it can be used in all international power grids.
- 4 Communication examples: HART® Communicator (handheld terminal), FieldXpert, Commubox FXA195 for intrinsically safe HART® communication with FieldCare via the USB interface, Bluetooth® technology with SmartBlue App.
- 5 FieldCare is a FDT-based plant asset management tool from Endress+Hauser, for details see section "accessories".

Modular design

Design		Options
	1: Terminal head	Variety of terminal heads made of aluminum, polyamide or stainless steel i Your benefits: <ul style="list-style-type: none"> Optimum terminal access thanks to low housing edge of bottom section: <ul style="list-style-type: none"> Easier to use Lower installation and maintenance costs Optional display: local process display for added reliability
	2: Wiring, electrical connection, output signal	<ul style="list-style-type: none"> Ceramic terminal block Flying leads Head transmitter: 4 to 20 mA, HART®, PROFIBUS® PA, FOUNDATION™ Fieldbus; IO-Link®, Ethernet-APL (single-channel or dual-channel) Attachable display
	3: Plug or cable gland	<ul style="list-style-type: none"> Polyamide or brass cable glands M12 plug, 4-pin/8-pin: PROFIBUS® PA, Ethernet-APL, IO-Link® 7/8" plug: PROFIBUS® PA, FOUNDATION™ Fieldbus
	4: Removable extension neck	Different extension neck options are available. <ul style="list-style-type: none"> Extension neck according to DIN 43772 QuickNeck Extension neck with second process seal Nipple, nipple-union, or nipple-union-nipple i Your benefits: iTHERM QuickNeck: tool-free removal of the insert: <ul style="list-style-type: none"> Saves time/costs on frequently calibrated measuring points Wiring mistakes avoided
	5: Lagging	The lagging of the thermowell provides space between the thermometer connection and the process connection.
	6: Process connection	Variety of process connections including threads, flanges according to EN or ASME standard, socket weld
	7: Thermowell	Versions with and without thermowell (for existing thermowells). <ul style="list-style-type: none"> Various diameters Various materials Various tip shapes (straight, tapered or stepped)
	8: Insert with: 8a: iTHERM QuickSens 8b: iTHERM StrongSens 8c: Central-spring-loaded insert	Sensor models: RTD - wire wound (WW), thin-film sensor (TF) or thermocouples type K, J or N. Insert diameter Ø3 mm (0.12 in) or Ø6 mm (0.24 in), depending on thermowell tip or selected thermometer i Your benefits: <ul style="list-style-type: none"> iTHERM QuickSens - insert with the world's fastest response time: <ul style="list-style-type: none"> Fast, highly accurate measurements, delivering maximum process safety and control Quality and cost optimization iTHERM StrongSens - insert with unbeatable durability: <ul style="list-style-type: none"> Vibration resistance ≤ 60g: lower life cycle costs thanks to longer operating life and high plant availability Automated, traceable production: top quality and maximum process safety




A0051655

2 Different thermowell versions available

- 1 For installation in a separate thermowell
- A Flanged, references acc. to ASME/Universal
- B With thread, references acc. to ASME/Universal
- C For weld-in, references acc. to ASME/Universal
- D Socket weld, references acc. to ASME/Universal

- E Length of removable extension neck - can be replaced (DIN extension neck, second process seal, nipple, etc.)
- T Length of thermowell lagging - lagging or extension neck, integral part of the thermowell
- U Immersion length - length of the lower thermometer section in the process medium, usually from the process connection



A0052349

3 Different thermowell versions available

- E* Flanged, references acc. to NAMUR
- G* For weld-in, references acc. to DIN
- M* Flanged, references acc. to DIN
- T* Flanged, iTHERM TwistWell

- E* Length of removable extension neck - can be replaced (DIN extension neck, second process seal, nipple, etc.)
- T* Length of thermowell lagging - lagging or extension neck, integral part of the thermowell
- U* Immersion length - length of the lower thermometer section in the process medium, usually from the process connection

Input

Measured variable Temperature (temperature linear transmission behavior)

Measuring range *Depends on the type of sensor used*

Sensor type	Measuring range
Pt100 thin-film (TF), basic iTHERM QuickSens, fast response	-50 to +200 °C (-58 to +392 °F)
Pt100 thin film (TF), standard	-50 to +400 °C (-58 to +752 °F)
Pt100 thin film (TF), iTHERM StrongSens, vibration-resistant ≤ 60g	-50 to +500 °C (-58 to +932 °F)
Pt100 wire wound (WW), extended measuring range	-200 to +600 °C (-328 to +1 112 °F)
Thermocouple TC, type J	-40 to +750 °C (-40 to +1 382 °F)
Thermocouple TC, type K	-40 to +1 100 °C (-40 to +2 012 °F)
Thermocouple TC, type N	

Output

Output signal Generally, the measured value can be transmitted in one of two ways:

- Directly-wired sensors - sensor measured values forwarded without a transmitter.
- Via all common protocols by selecting an appropriate Endress+Hauser iTEMP transmitter. All the transmitters listed below are mounted directly in the terminal head and wired with the sensory mechanism.

Family of temperature transmitters

Thermometers fitted with iTEMP transmitters are an installation-ready complete solution to improve temperature measurement by significantly increasing accuracy and reliability, when compared to direct wired sensors, as well as reducing both wiring and maintenance costs.

4 to 20 mA head transmitters

They offer a high degree of flexibility, thereby supporting universal application with low inventory storage. The iTEMP transmitters can be configured quickly and easily at a PC. Endress+Hauser offers free configuration software which can be downloaded from the Endress+Hauser Website.

HART® head transmitters

The transmitter is a 2-wire device with one or two measuring inputs and one analog output. The device not only transfers converted signals from resistance thermometers and thermocouples, it also transfers resistance and voltage signals using HART® communication. Swift and easy operation, visualization and maintenance using universal configuration software like FieldCare, DeviceCare or FieldCommunicator 375/475. Integrated Bluetooth® interface for the wireless display of measured values and configuration via Endress +Hauser SmartBlue (app), optional.

PROFIBUS® PA head transmitters

Universally programmable head transmitter with PROFIBUS® PA communication. Conversion of various input signals into digital output signals. High measurement accuracy over the complete ambient temperature range. PROFIBUS PA functions and device-specific parameters are configured via fieldbus communication.

FOUNDATION Fieldbus™ head transmitters

Universally programmable head transmitter with FOUNDATION Fieldbus™ communication. Conversion of various input signals into digital output signals. High measurement accuracy over the complete ambient temperature range. All transmitters are approved for use in all the main process control systems. The integration tests are performed in Endress+Hauser's 'System World'.

Head transmitter with PROFINET® and Ethernet-APL

The temperature transmitter is a 2-wire device with two measuring inputs. The device not only transfers converted signals from resistance thermometers and thermocouples, it also transfers resistance and voltage signals using the PROFINET® protocol. Power is supplied via the 2-wire

Ethernet connection according to IEEE 802.3cg 10Base-T1. The transmitter can be installed as an intrinsically safe electrical apparatus in Zone 1 hazardous areas. The device can be used for instrumentation purposes in the terminal head form B (flat face) according to DIN EN 50446.


Head transmitter with IO-Link®

The temperature transmitter is an IO-Link® device with a measurement input and an IO-Link® interface. It offers a configurable, simple and cost-effective solution thanks to digital communication via IO-Link®. The device is mounted in a terminal head form B (flat face) as per DIN EN 5044.

Advantages of the iTEMP transmitters:


- Dual or single sensor input (optionally for certain transmitters)
- Attachable display (optionally for certain transmitters)
- Unsurpassed reliability, accuracy and long-term stability in critical processes
- Mathematical functions
- Monitoring of the thermometer drift, sensor backup functionality, sensor diagnostic functions
- Sensor-transmitter-matching based on the Callendar van Dusen coefficients (CvD).

Power supply


 The sensor connection wires are equipped with terminal lugs. The nominal diameter of the cable lug is 1.3 mm (0.05 in)

Terminal assignment


Type of sensor connection RTD



A0045453

 4 Mounted ceramic terminal block


- 1 3-wire
- 2 2x3-wire
- 3 4-wire
- 4 Outside screw



A0045464

 5 Head mounted transmitter TMT7x or TMT31 (single input)


- 1 Sensor input, RTD, 4-, 3- and 2-wire
- 2 Power supply/bus connection
- 3 Display connection/CDI interface



A0052495

6 Head-mounted transmitter TMT36 (single input)

- 1 RTD sensor input: 4-, 3- and 2-wire
- 2 Display connection
- L+ 18 to 30 V_{DC} power supply
- L- 0 V_{DC} power supply
- C/Q IO-Link or switch output




A0045466

7 Head-mounted transmitter TMT8x (dual sensor input)

- 1 Sensor input 1, RTD, 4- and 3-wire
- 2 Sensor input 2, RTD, 3-wire
- 3 Fieldbus connection and power supply
- 4 Display connection


Mounted field transmitter: Fitted with screw terminals



A0045732

8 TMT162 (dual input)

- 1 Sensor input 1, RTD: 3- and 4-wire
- 2 Sensor input 2, RTD: 3-wire
- 3 Field transmitter power supply and analog output 4 to 20 mA or fieldbus connection




A0045733

9 TMT142B (single input)


- 1 Sensor input RTD
- 2 Power supply field transmitter and analog output 4 to 20 mA, HART® signal
- 3 2-wire
- 4 3-wire
- 5 4-wire

Type of sensor connection thermocouple (TC)



A0012700


10 Mounted ceramic terminal block



A0045474

11 Head-mounted transmitter TMT8x (dual sensor input)


- 1 Sensor input 1
- 2 Sensor input 2
- 3 Fieldbus connection and power supply
- 4 Display connection



A0045353

12 Head-mounted transmitter TMT7x (single input)

- 1 Sensor input
- 2 Power supply and bus connection
- 3 Display connection and CDI interface



A0045636

13 Mounted field transmitter TMT162 or TMT142B

- 1 Sensor input 1
- 2 Sensor input 2 (not TMT142B)
- 3 Supply voltage for field transmitter and analog output 4 to 20 mA or fieldbus communication

Thermocouple wire colors

As per IEC 60584	As per ASTM E230
<ul style="list-style-type: none"> ▪ Type J: black (+), white (-) ▪ Type K: green (+), white (-) ▪ Type N: pink (+), white (-) 	<ul style="list-style-type: none"> ▪ Type J: white (+), red (-) ▪ Type K: yellow (+), red (-) ▪ Type N: orange (+), red (-)


Integrated overvoltage protection

Overvoltage protection is optionally available¹⁾. The module protects the electronics from damage from overvoltage. Overvoltage occurring in signal cables (e.g. 4 to 20 mA, communication lines (fieldbus systems) and power supply is diverted to ground. The functionality of the transmitter is not affected as no problematic voltage drop occurs.

Connection data:

Maximum continuous voltage (rated voltage)	$U_C = 36 V_{DC}$
Nominal current	$I = 0.5 A$ at $T_{amb.} = 80\text{ °C}$ (176 °F)
Surge current resistance <ul style="list-style-type: none"> ▪ Lightning surge current D1 (10/350 μs) ▪ Nominal discharge current C1/C2 (8/20 μs) 	<ul style="list-style-type: none"> ▪ $I_{imp} = 1\text{ kA}$ (per wire) ▪ $I_n = 5\text{ kA}$ (per wire) ▪ $I_n = 10\text{ kA}$ (total)
Temperature range	-40 to +80 °C (-40 to +176 °F)
Series resistance per wire	1.8 Ω , tolerance $\pm 5\%$

1) Available for the field transmitters with HART® 7 communication



A0045614

14 Electrical connection of surge arrester

- 1 Sensor connection 1
- 2 Sensor connection 2
- 3 Bus terminator and power supply

The device must be connected to the potential equalization via the external ground clamp. The connection between the housing and the local ground must have a minimum cross-section of 4 mm² (13 AWG). All ground connections must be secured tightly.

Terminals

iTEMP head transmitters fitted with push-in terminals unless screw terminals are explicitly selected, the second process seal is chosen or a double sensor is installed.

Cable entries

See "Terminal heads" section.

The cable entries must be selected during the configuration of the device. Different terminal heads offer different possibilities with regard to threads and the number of available cable entries.

Connectors

Endress+Hauser offers a wide variety of connectors for the simple and fast integration of the thermometer into a process control system. The following tables show the PIN assignments of the various plug connector combinations.

i We do not recommend connecting thermocouples directly to connectors. The direct connection to the pins of the plug might generate a new 'thermocouple' which influences the accuracy of the measurement. Therefore we do not connect thermocouples directly to connectors. The thermocouples are connected in combination with a transmitter.

Abbreviations

#1	Order: first transmitter/insert	#2	Order: second transmitter/insert
i	Insulated. Wires marked 'I' are not connected and are insulated with heat shrink tubes.	YE	Yellow
GND	Grounded. Wires marked 'GND' are connected to the internal grounding screw in the terminal head.	RD	Red
BN	Brown	WH	White
GNYE	Green-yellow	PK	Pink
BU	Blue	GN	Green
GY	Gray	BK	Black

Terminal head with one cable entry



Plug	1x PROFIBUS® PA								1x FOUNDATION™ Fieldbus (FF)				1x PROFINET® and Ethernet-APL			
	M12				7/8"				7/8"				M12			
PIN number	1	2	3	4	1	2	3	4	1	2	3	4	1	2	3	4

Plug	1x PROFIBUS® PA								1x FOUNDATION™ Fieldbus (FF)				1x PROFINET® and Ethernet-APL			
Electrical connection (terminal head)																
Flying leads and TC	Not connected (not insulated)															
3-wire terminal block (1x Pt100)	RD	RD	WH		RD	RD	WH		RD	RD	WH		RD	RD	WH	
4-wire terminal block (1x Pt100)			WH	WH			WH	WH			WH	WH				
6-wire terminal block (2x Pt100)	RD (#1) ¹	RD (#1)	WH (#1)		RD (#1)	RD (#1)	WH (#1)		RD (#1)	RD (#1)	WH (#1)				WH (#1)	
1x TMT 4 to 20 mA or HART®	+	i	-	i	+	i	-	i	+	i	-	i	+	i	-	i
2x TMT 4 to 20 mA or HART® in the terminal head with a high cover	+(#1)	+(#2)	-(#1)	- (#2)	+(#1)	+(#2)	-(#1)	- (#2)	+(#1)	+(#2)	-(#1)	-(#2)	+(#1)	+(#2)	-(#1)	-(#2)
1x TMT PROFIBUS® PA	+	i	-	GND ²⁾	+	i	-	GND ²⁾	Cannot be combined							
2x TMT PROFIBUS® PA	+(#1)		-(#1)		+		-									
1x TMT FF	Cannot be combined				Cannot be combined				-	+	GND	i	Cannot be combined			
2x TMT FF									-(#1)	+(#1)						
1x TMT PROFINET®	Cannot be combined				Cannot be combined				Cannot be combined				APL signal -	APL signal +	GND	-
2x TMT PROFINET®													APL signal - (#1)	APL signal + (#1)		
PIN position and color code																


- 1) Second Pt100 is not connected
- 2) If using a head without a grounding screw, e.g. plastic housing TA30S or TA30P, insulated 'i' instead of grounded GND

Terminal head with one cable entry


Plug	4-pin/8-pin							
Plug thread	M12							
PIN number	1	2	3	4	5	6	7	8
Electrical connection (terminal head)								
Flying leads and TC	Not connected (not insulated)							
3-wire terminal block (1x Pt100)	RD	RD	WH		i			
4-wire terminal block (1x Pt100)			WH	WH				
6-wire terminal block (2x Pt100)			WH		BK	BK	YE	
1x TMT 4 to 20 mA or HART®	+(#1)	i	-(#1)	i	i			
2x TMT 4 to 20 mA or HART® in the terminal head with a high cover								
1x TMT PROFIBUS® PA	Cannot be combined							





Plug	4-pin/8-pin	
2x TMT PROFIBUS® PA		
1x TMT FF	Cannot be combined	
2x TMT FF		
1x TMT PROFINET®	Cannot be combined	
2x TMT PROFINET®	Cannot be combined	
PIN position and color code	 <p>1 BN 2 GNYE 3 BU 4 GY</p> <p>A0018929</p>	 <p>1 WH 2 BN 3 GN 4 YE 5 GY 6 PK 7 BU 8 RD</p> <p>A0018927</p>

Terminal head with one cable entry


Plug	1x IO-Link®, 4-pin			
Plug thread	M12			
PIN number	1	2	3	4
Electrical connection (terminal head)				
Flying leads	Not connected (not insulated)			
3-wire terminal block (1x Pt100)	RD	i	RD	WH
4-wire terminal block (1x Pt100)	Cannot be combined			
6-wire terminal block (2x Pt100)	Cannot be combined			
1x TMT 4 to 20 mA or HART®	Cannot be combined			
2x TMT 4 to 20 mA or HART® in the terminal head with a high cover	Cannot be combined			
1x TMT PROFIBUS® PA	Cannot be combined			
2x TMT PROFIBUS® PA	Cannot be combined			
1x TMT FF	Cannot be combined			
2x TMT FF	Cannot be combined			
1x TMT PROFINET®	Cannot be combined			
2x TMT PROFINET®	Cannot be combined			
1x TMT IO-Link®	L+	-	L-	C/Q
2x TMT IO-Link®	L+ (#1)	-	L- (#1)	C/Q
PIN position and color code	 <p>1 BN 3 BU 4 BK</p> <p>A0055383</p>			



Terminal head with two cable entries

Plug	2x PROFIBUS® PA				2x FOUNDATION™ Fieldbus (FF)				2x PROFINET® and Ethernet-APL							
Plug thread	M12(#1) / M12(#2)				7/8"(#1)/7/8"(#2)				7/8"(#1)/7/8"(#2)				M12 (#1)/M12 (#2)			
 <p>A0021706</p>																
PIN number	1	2	3	4	1	2	3	4	1	2	3	4	1	2	3	4


Plug	2x PROFIBUS® PA								2x FOUNDATION™ Fieldbus (FF)				2x PROFINET® and Ethernet-APL			
Electrical connection (terminal head)																
Flying leads and TC	Not connected (not insulated)															
3-wire terminal block (1x Pt100)	RD/i	RD/i	WH/i		RD/i	RD/i	WH/i		RD/i	RD/i	WH/i		RD/i	RD/i	WH/i	
4-wire terminal block (1x Pt100)			WH/i	WH/i			WH/i	WH/i			WH/i	WH/i			WH/i	WH/i
6-wire terminal block (2x Pt100)	RD/B K	RD/B K	WH/YE		RD/B K	RD/B K	WH/YE		RD/B K	RD/B K	WH/YE		RD/B K	RD/B K	WH/YE	
1x TMT 4 to 20 mA or HART®	+/i		-/i		+/i		-/i		+/i		-/i		+/i		-/i	
2x TMT 4 to 20 mA or HART® in the terminal head with a high cover	+ (#1)/ + (#2)	i/i	- (#1)/ - (#2)	i/i	+ (#1)/ + (#2)	i/i	- (#1)/ - (#2)	i/i	+ (#1)/ + (#2)	i/i	- (#1)/ - (#2)	i/i	+ (#1)/ + (#2)	i/i	- (#1)/ - (#2)	i/i
1x TMT PROFIBUS® PA	+/i		-/i		+/i		-/i		Cannot be combined							
2x TMT PROFIBUS® PA	+ (#1)/ + (#2)		- (#1)/ - (#2)	GND/ GND	+ (#1)/ + (#2)		- (#1)/ - (#2)	GND/ GND								
1x TMT FF	Cannot be combined		Cannot be combined		-/i	+/i							Cannot be combined			
2x TMT FF	Cannot be combined		Cannot be combined		- (#1)/ - (#2)	+ (#1)/ + (#2)	i/i	GND/ GND	Cannot be combined							
1x TMT PROFINET®	Cannot be combined		Cannot be combined		Cannot be combined				APL signal -	APL signal +						
2x TMT PROFINET®	Cannot be combined		Cannot be combined		Cannot be combined				APL signal - (#1) and (#2)	APL signal + (#1) and (#2)	GND	i				
PIN position and color code	 4 3 1 2 1 BN 2 GNYE 3 BU 4 GY <small>A0018929</small>		 1 3 2 4 1 BN 2 GNYE 3 BU 4 GY <small>A0018930</small>		 1 3 2 4 1 BU 2 BN 3 GY 4 GNYE <small>A0018931</small>		 4 3 1 2 1 RD 2 GN <small>A0052119</small>									

Terminal head with two cable entries

Plug	4-pin/8-pin							
Plug thread	M12 (#1)/M12 (#2)							
 #1 #2 <small>A0021706</small>								
PIN number	1	2	3	4	5	6	7	8
Electrical connection (terminal head)								
Flying leads and TC	Not connected (not insulated)							
3-wire terminal block (1x Pt100)	RD/i	RD/i	WH/i			i/i		

Plug	4-pin/8-pin				
4-wire terminal block (1x Pt100)			WH/i	WH/i	
6-wire terminal block (2x Pt100)	RD/BK	RD/BK	WH/YE		
1x TMT 4 to 20 mA or HART®	+/i	i/i	-/i	i/i	
2x TMT 4 to 20 mA or HART® in the terminal head with a high cover	+(#1)/+(#2)		-(#1)/-(#2)		
1x TMT PROFIBUS® PA	Cannot be combined				
2x TMT PROFIBUS® PA					
1x TMT FF	Cannot be combined				
2x TMT FF					
1x TMT PROFINET®	Cannot be combined				
2x TMT PROFINET®	Cannot be combined				
PIN position and color code	 <p>1 BN 2 GNYE 3 BU 4 GY</p>			 <p>1 WH 2 BN 3 GN 4 YE 5 GY 6 PK 7 BU 8 RD</p>	

Terminal head with two cable entries

Plug	2x IO-Link®, 4-pin			
Plug thread	M12(#1)/M12 (#2)			
PIN number	1	2	3	4
Electrical connection (terminal head)				
Flying leads	Not connected (not insulated)			
3-wire terminal block (1x Pt100)	RD	i	RD	WH
4-wire terminal block (1x Pt100)	Cannot be combined			
6-wire terminal block (2x Pt100)	RD/BK	i	RD/BK	WH/YE
1x TMT 4 to 20 mA or HART®	Cannot be combined			
2x TMT 4 to 20 mA or HART® in the terminal head with a high cover				
1x TMT PROFIBUS® PA	Cannot be combined			
2x TMT PROFIBUS® PA				
1x TMT FF	Cannot be combined			
2x TMT FF				
1x TMT PROFINET®	Cannot be combined			
2x TMT PROFINET®				
1x TMT IO-Link®	L+	-	L-	C/Q
2x TMT IO-Link®	L+ (#1) and (#2)	-	L- (#1) and (#2)	C/Q
PIN position and color code	 <p>1 BN 3 BU 4 BK</p>			

Connection combination: insert - transmitter

Insert	Transmitter connection ¹⁾			
	TMT31/TMT7x		TMT8x	
	1x 1-channel	2x 1-channel	1x 2-channel	2x 2-channel
1x sensor (Pt100 or TC), flying leads	Sensor (#1) : transmitter (#1)	Sensor (#1) : transmitter (#1) (Transmitter (#2) not connected)	Sensor (#1) : transmitter (#1)	Sensor (#1) : transmitter (#1) Transmitter (#2) not connected
2x sensor (2x Pt100 or 2x TC), flying leads	Sensor (#1) : transmitter (#1) Sensor (#2) insulated	Sensor (#1) : transmitter (#1) Sensor (#2): transmitter (#2)	Sensor (#1) : transmitter (#1) Sensor (#2): transmitter (#1)	Sensor (#1) : transmitter (#1) Sensor (#2): transmitter (#1) (Transmitter (#2) not connected)
1x sensor (Pt100 or TC), with terminal block ²⁾	Sensor (#1) : transmitter in cover	Cannot be combined	Sensor (#1) : transmitter in cover	Cannot be combined
2x sensor (2x Pt100 or 2x TC) with terminal block	Sensor (#1) : transmitter in cover Sensor (#2) not connected		Sensor (#1) : transmitter in cover Sensor (#2): transmitter in cover	
2x sensors (2x Pt100 or 2x TC) in conjunction with feature 600, option MG ³⁾	Cannot be combined	Sensor (#1) : transmitter (#1) Sensor (#2): transmitter (#2)	Cannot be combined	Sensor (#1): transmitter (#1) - channel 1 Sensor (#2): transmitter (#2) - channel 1

- 1) If 2 transmitters are selected in a terminal head, transmitter (#1) is installed directly on the insert. Transmitter (#2) is installed in the high cover. A TAG cannot be ordered for the second transmitter as standard. The bus address is set to the default value and, if necessary, must be changed manually before commissioning.
- 2) Only in the terminal head with a high cover, only 1 transmitter possible. A ceramic terminal block is automatically fitted on the insert.
- 3) Individual sensors each connected to channel 1 of a transmitter

Surge arrester

To protect against overvoltage in the power supply and signal/communication cables for the thermometer electronics, Endress+Hauser offers the HAW562 surge arrester for DIN rail mounting and the HAW569 for field housing installation.




For more information, see the Technical Information "HAW562 Surge arrester" TI01012K and "HAW569 Surge arrester" TI01013K.

Performance characteristics

Reference conditions

These data are relevant for determining the measurement accuracy of the transmitters used. For details, see the relevant Technical Information.

Maximum measurement error RTD resistance thermometer or assembly as per IEC 60751



1) |t| = absolute temperature value in °C

To obtain the maximum tolerances in °F, multiply the results in °C by a factor of 1.8.

Temperature ranges

Sensor type ¹⁾	Operating temperature range	Class B	Class A	Class AA
Pt100 (TF) Basic	-50 to +200 °C (-58 to +392 °F)	-50 to +200 °C (-58 to +392 °F)	-30 to +200 °C (-22 to +392 °F)	-
Pt100 (TF) Standard	-50 to +400 °C (-58 to +752 °F)	-50 to +400 °C (-58 to +752 °F)	-30 to +250 °C (-22 to +482 °F)	0 to +150 °C (32 to 302 °F)
Pt100 (TF) iTHERM QuickSens	-50 to +200 °C (-58 to +392 °F)	-50 to +200 °C (-58 to +392 °F)	-30 to +200 °C (-22 to +392 °F)	0 to +150 °C (32 to 302 °F)
Pt100 (TF) iTHERM StrongSens	-50 to +500 °C (-58 to +932 °F)	-50 to +500 °C (-58 to +932 °F)	-30 to +300 °C (-22 to +572 °F)	0 to +150 °C (+32 to +302 °F)
Pt100 (WW)	-200 to +600 °C (-328 to +1112 °F)	-200 to +600 °C (-328 to +1112 °F)	-100 to +450 °C (-148 to +842 °F)	-50 to +250 °C (-58 to +482 °F)

1) Selection depending on product and configuration

Influence of ambient temperature

Depends on the head transmitter used. For details, see the relevant Technical Information.

Self-heating

RTD elements are passive resistors that are measured using an external current. This measurement current causes a self-heating effect in the RTD element itself, which in turn creates an additional measurement error. In addition to the measurement current, the size of the measurement error is also affected by the temperature conductivity and flow velocity of the process. This self-heating error is negligible when an Endress+Hauser iTEMP transmitter (very small measurement current) is connected.

Calibration**Calibration of thermometers**

Calibration involves comparing the measured values of a unit under test (UUT) with those of a more precise calibration standard using a defined and reproducible measurement method. The aim is to determine the deviation of the UUT's measured values from the true value of the measured variable. Two different methods are used for thermometers:

- Calibration at fixed-point temperatures, e.g. at the freezing point of water at 0 °C,
- Calibration compared against a precise reference thermometer.

The thermometer to be calibrated must display the fixed point temperature or the temperature of the reference thermometer as accurately as possible. Temperature-controlled calibration baths with very homogeneous thermal values, or special calibration furnaces are typically used for thermometer calibrations. The measurement uncertainty may increase due to heat conduction errors and short immersion lengths. The existing measurement uncertainty is recorded on the individual calibration certificate. For accredited calibrations in accordance with ISO17025, a measurement uncertainty that is twice as high as the accredited measurement uncertainty is not permitted. If this limit is exceeded, only a factory calibration is possible.

Evaluation of thermometers

If a calibration with an acceptable measurement uncertainty and transferable measurement results is not possible, Endress+Hauser offers customers a thermometer evaluation measurement service, if technically feasible. This is the case when:

- The process connections/flanges are too big or the immersion length (IL) is too short to allow the UUT to be immersed sufficiently in the calibration bath or furnace (see the following table), or
- Due to heat conduction along the thermometer tube, the resulting sensor temperature generally deviates significantly from the actual bath/furnace temperature.

The measured value of the UUT is determined using the maximum possible immersion depth and the specific measuring conditions and measurement results are documented on an evaluation certificate.

Sensor-transmitter-matching

The resistance/temperature curve of platinum resistance thermometers is standardized but in practice it is rarely possible to keep to the values precisely over the entire operating temperature range. For this reason, platinum resistance sensors are divided into tolerance classes, such as Class A, AA or B as per IEC 60751. These tolerance classes describe the maximum permissible deviation of the specific sensor characteristic curve from the standard curve, i.e. the maximum temperature-dependent characteristic error that is permitted. The conversion of measured sensor resistance values to temperatures in temperature transmitters or other meter electronics is often susceptible to considerable errors as the conversion is generally based on the standard characteristic curve.

When Endress +Hauser temperature transmitters are used, this conversion error can be reduced significantly by sensor-transmitter matching:

- Calibration at three temperatures at least and determination of the actual temperature sensor characteristic curve,
- Adjustment of the sensor-specific polynomial function using Calendar-van Dusen (CvD) coefficients,
- Configuration of the temperature transmitter with the sensor-specific CvD coefficients for resistance/temperature conversion, and
- another calibration of the reconfigured temperature transmitter with connected resistance thermometer.

Endress+Hauser offers its customers this kind of sensor-transmitter matching as a separate service. Furthermore, the sensor-specific polynomial coefficients of platinum resistance thermometers are always provided on every Endress+Hauser calibration certificate where possible, e.g. at least three calibration points, so that users themselves can also appropriately configure suitable temperature transmitters.

For the device, Endress+Hauser offers standard calibrations at a reference temperature of -80 to +600 °C (-112 to +1 112 °F) based on the ITS90 (International Temperature Scale). Calibrations in other temperature ranges are available from your Endress+Hauser sales center on request. Calibrations are traceable to national and international standards. The calibration certificate is referenced to the serial number of the device. Only the insert is calibrated.

Minimum immersion length (IL) for inserts required to perform a correct calibration

i Due to the limitations of furnace geometries, the minimum insertion lengths must be observed at high temperatures to enable a calibration to be performed with an acceptable degree of measurement uncertainty. The same applies when using a head transmitter. Due to heat conduction, minimum lengths must be observed in order to guarantee the functionality of the transmitter -40 to +85 °C (-40 to +185 °F)

Calibration temperature	Minimum immersion length IL in mm without head transmitter
-196 °C (-320.8 °F)	120 mm (4.72 in) ¹⁾
-80 to +250 °C (-112 to +482 °F)	No minimum immersion length required ²⁾
251 to 550 °C (483.8 to 1022 °F)	300 mm (11.81 in)
551 to 600 °C (1023.8 to 1 112 °F)	400 mm (15.75 in)

- 1) with iTEMP head transmitter min. 150 mm (5.91 in) is required
- 2) at a temperature of 80 to 250 °C (176 to 482 °F), the iTEMP head transmitter requires min. 50 mm (1.97 in)

Insulation resistance


- RTD: Insulation resistance according to IEC 60751 > 100 MΩ at 25 °C between terminals and sheath material measured with a minimum test voltage of 100 V DC
- TC: Insulation resistance according to IEC 1515 between terminals and sheath material with a test voltage of 500 V DC:
 - > 1 GΩ at 20 °C
 - > 5 MΩ at 500 °C

Installation

Orientation

No restrictions. However, self-draining in the process should be guaranteed depending on the application.

Installation instructions



15 Installation examples

- 1 - 2 In pipes with a small cross-section, the sensor tip should reach or extend slightly past the center axis of the pipe (=U).
- 3 - 4 Slanted orientation.

The immersion length of the thermometer influences the measurement accuracy. If the immersion length is too small, errors in the measurement are caused by heat conduction via the process connection and the container wall. Therefore, if installing in a pipe the immersion length should be at least half the pipe diameter. Installation at an angle (see item 3 and 4) could be another solution. When determining the immersion length, all the parameters of the thermometer and of the process to be measured must be taken into account (e.g. flow velocity, process pressure).

For the best installation, apply the following rule: $h \sim d$; $U > D/2 + h$.

The counterparts for process connections and seals are not supplied with the thermometer and must be ordered separately if needed.

Ambient conditions

Ambient temperature range	Terminal head	Temperature in °C (°F)
	Without mounted head transmitter	Depends on the terminal head used and the cable gland or fieldbus connector; see "Terminal heads" section.
	With mounted head transmitter	-40 to +85 °C (-40 to +185 °F)
	With mounted head transmitter and display	-20 to +70 °C (-4 to +158 °F)
Storage temperature	For information, see the ambient temperature above.	
Humidity	Depends on the transmitter used. If Endress+Hauser iTHERM head transmitters are used: <ul style="list-style-type: none"> ■ Condensation permitted as per IEC 60 068-2-33 ■ Max. rel. humidity: 95% as per IEC 60068-2-30 	
Climate class	As per EN 60654-1, Class C	
Degree of protection	Max. IP 66 (NEMA Type 4x encl.)	Depending on the design (terminal head, connector, etc.).
	Partly IP 68	Tested in 1.83 m (6 ft) over 24 h
Shock and vibration resistance	The Endress+Hauser inserts exceed the requirements of IEC 60751 with regard to shock and vibration resistance of 3g in a range of 10 to 500 Hz. The vibration resistance of the measuring point depends on the sensor type and design. Refer to the following table:	
	Sensor type	Vibration resistance for the sensor tip
	Pt100 (WW)	≤ 30 m/s ² (3g)
	Pt100 (TF), basic	
	Pt100 (TF), standard	≤ 40 m/s ² (4g)
	iTHERM StrongSens Pt100 (TF)	≤ 600 m/s ² (60g)
	iTHERM QuickSens Pt100 (TF), version: Ø6 mm (0.24 in)	≤ 600 m/s ² (60g)
	iTHERM QuickSens Pt100 (TF), version: Ø3 mm (0.12 in)	≤ 30 m/s ² (3g)
	Thermocouple inserts	≤ 30 m/s ² (3g)
Electromagnetic compatibility (EMC)	Depends on the head transmitter used. For details, see the relevant Technical Information.	

Process


Process temperature range Depends on the sensor type and the thermowell material used,

max. -200 to +1 100 °C (-328 to +2 012 °F)

for fast-response thermowell max. -200 to +400 °C (-328 to +752 °F)

Process pressure range

The maximum possible process pressure depends on various influencing factors, such as the design, process connection and process temperature. For information on the maximum possible process pressures for the individual process connections, see the "Process connection" section.

 It is possible to check the mechanical loading capacity as a function of the installation and process conditions online using the Sizing Thermowell calculation tool in the Endress+Hauser Applicator software. <https://portal.endress.com/webapp/applicator>

Permitted flow velocity depending on the immersion length

The highest flow velocity tolerated by the thermometer diminishes with increasing sensor immersion length exposed to the flowing fluid. In addition it is dependent on the diameter of both the thermometer tip and thermowell, on the type of measuring medium, the process temperature and the process pressure.


Process connection	Standard	Max. process pressure
Weld-in version/ socket weld	-	≤ 500 bar (7 252 psi)
Flange	EN1092-1 or ISO 7005-1	Depending on the flange pressure rating PNxx: 20, 40, 50 or 100 bar at 20 °C (68 °F)
	ASME B16.5	Depending on the flange pressure rating 150, 300, 600, 900/1500 or 2500 psi at 20 °C (68 °F)
	JIS B 2220	Depending on the flange pressure rating 10K
Thread	ISO 965-1 / ASME B1.13M ISO 228-1 ANSI B1.20.1 DIN EN 10226-1 / JIS B 0203	140 bar (2 031 psi) at +40 °C (+140 °F) 85 bar (1 233 psi) at +400 °C (+752 °F)


Mechanical construction

Design, dimensions

All dimensions in mm (in). The design of the thermometer depends on the general design version used:

- Thermometer for installation in a separate thermowell
- Thermometer with thermowell, based on ASME: ANSI flanges, NPT thread, socket weld and weld-in version
- Thermometer with thermowell, based on DIN: EN flanges, M-thread or G-thread, socket weld and weld-in version
- Thermometer with thermowell, based on NAMUR and TwistWell, flanges

 It is possible to check the mechanical loading capacity depending on the installation and process conditions online in the TW Sizing Module for thermowells in the Endress+Hauser Applicator software. See "Accessories" section.

 Various dimensions, such as the immersion length U, the lagging length T and the extension neck length E, for example, are variable values and are therefore indicated as items in the following dimensional drawings.

Variable dimensions:

Item	Description
E	Extension neck length, variable depending on the configuration or pre-defined for the version with iTHERM QuickNeck
IL	Insertion length of insert
L	Thermowell length (U+T)
T	Length of lagging: variable or predefined, depends on thermowell version (see also the individual table data)

Item	Description
U	Immersion length: variable, depending on the configuration
L_Gp	Thread length (complete thread length)
L_Gp_e	Thread engagement length
Gp	Process connection thread
B	Thermowell bottom thickness (default value 6 mm (0.24 in) - other thickness optionally available)
D1	Root diameter
D2	Tip diameter
C1	Length of the tapered part
Re1	Stepped length of tip
Di1	Bore diameter
Di2	Bore diameter tip
De1	Lagging diameter
Ge1	Thermometer connection thread
Hd, SL	Variable for calculating the insertion length of the insert, depending on different screw-in lengths in terminal head thread M24x1.5 or ½" NPT, see insert length calculation (IL). <div style="text-align: center;"> </div> <p>16 Different screw-in lengths in terminal head thread for M24x1.5 and ½" NPT</p> <p>1 Metric thread M24x1.5 2 Conical thread NPT ½"</p> <p>Hd Distance in terminal head SL Spring pre-load</p>
GC	Gasket compensation only for metric threads


Thermometer for installation in a separate thermowell

The thermometer is supplied without a thermowell but is designed for use with a thermowell.




This version cannot be used for direct immersion in the process medium!


The thermometer can be configured as follows



A0051677



A0052795



A0051681

- Option A: without extension neck (female thread M24, M20x1.5 or NPT ½")¹⁾
- Option B, C, D, E: removable extension neck; metric thread for connection to thermowell must be selected
- Option F (DIN-style): QuickNeck upper part iTHERM TS111
- Option F (ASME-style): QuickNeck upper part with iTHERM TS211
- Option G (DIN-style): QuickNeck, complete, with iTHERM TS111
- Option G (ASME-style): QuickNeck, complete, with iTHERM TS211
- Option H: extension neck with second process seal (thread M24x1.5 female fitting to thermowell) or with male thread, metric or NPT ½"
- Options L, M, N: NPT ½" nipple, nipple-union or nipple-union-nipple connection

1) Configuration feature 50: process/thermowell connection

Calculation of insert length IL


Option A: without neck	IL = U + Hd
Option A for use with NAMUR thermowell	Thermowell TT151 type NF1: UTM151 = 304 mm (11.97 in); IL = 315 mm (12.4 in) Thermowell TT151 type NF2: UTM151 = 364 mm (14.33 in); IL = 375 mm (14.8 in) Thermowell TT151 type NF3: UTM151 = 424 mm (16.7 in); IL = 435 mm (17.13 in)
Options B, C, D, E: removable extension neck	Metric thread version: IL = U + E + Hd + GC NPT thread version: IL = U + E + Hd
Option F (DIN-style): QuickNeck, upper part	IL = U + E + Hd Length E = 28 mm (1.10 in) for M24x1.5 to terminal head Length E = 21 mm (0.83 in) for NPT ½" to terminal head
Option F (ASME-style): QuickNeck, upper part	IL = U + E + Hd Length E = 46 mm (1.81 in) for M24x1.5 to terminal head Length E = 44 mm (1.73 in) for NPT ½" to terminal head
Option G (DIN-style): QuickNeck, complete	DIN-style: Thermowell connection as cylindrical thread (M14; M18; G½") IL = U + E + Hd + GC Length E = 74 mm (2.91 in) for M24x1.5 to terminal head Length E = 68 mm (2.68 in) for NPT ½" to terminal head
Option G (ASME-style): QuickNeck, complete	ASME-style: Thermowell connection as conical thread (NPT ½") IL = U + E + Hd + GC Length E = 101 mm (3.98 in)
Option H: second process seal	Thermowell connection as internal thread M24x1.5 IL = U + E + Hd + GC Length E = 56 mm (2.2 in) for M24x1.5 to terminal head Length E = 48 mm (1.89 in) for NPT ½" to terminal head
	Thermowell connection as cylindrical thread (M14; M18; G½") IL = U + E + Hd + GC Length E = 85 mm (3.35 in) for M24x1.5 to terminal head Length E = 76 mm (3 in) for NPT ½" to terminal head

	Thermowell connection as conical thread NPT 1/2" IL = U + E + Hd Length E = 147 mm (5.79 in) for application: Non-Ex, Ex ia, GP, IS Length E = 158 mm (6.22 in) for application: Ex d, XP
Options L, M, N: nipple connection	IL = U + E + Hd
Hd for head thread M24x1.5 (TA30A, TA30D, TA30P, TA30R, TA20AB) = 11 mm (0.43 in) Hd for head thread NPT 1/2" (TA30EB) = 26 mm (1.02 in) Hd for head thread NPT 1/2" (TA30H) = 41 mm (1.61 in) GC seal compensation = 2 mm (0.08 in)	

Thermometer with thermowell according to ASME standard

The thermometer always has a thermowell.

The thermometer can be configured as follows²⁾



A0051907

- Option A: based on ASME B40.9, with flange
- Option B: based on ASME B40.9, with thread
- 1: NPT thread
- 2: Metric thread
- Option C: based on ASME B40.9, for weld-in
- Option D: based on ASME B40.9, with socket weld

2) See also configuration feature O20/O30: Thermowell/thermometer structure


Calculation of insert length IL

		Application Non-Ex/Ex ia/GP/IS	Application Ex d/XP
Version A	$IL = U + T + E + Hd - B + SL$ SL = spring pre-load = 6 mm (0.24 in) B = 6 mm (0.24 in)	Hd = -17 mm (-0.67 in) E = 101 mm (3.98 in)	Hd = 10 mm (0.39 in) E = 101 mm (3.98 in)
Version B	$IL = U + T + E + Hd - B + SL$ SL = spring pre-load = 6 mm (0.24 in) B = 6 mm (0.24 in)	Hd = -17 mm (-0.67 in) E = 147 mm (5.79 in)	Hd = 10 mm (0.39 in) E = 158 mm (6.22 in)
Version C	$IL = U + T + E + Hd - B + SL$ SL = spring pre-load = 6 mm (0.24 in) B = 6 mm (0.24 in)	Hd = -17 mm (-0.67 in) E = 35 mm (1.38 in)	Hd = 10 mm (0.39 in) E = 47 mm (1.85 in)
Version D	$IL = U + T + E + Hd - B + SL$ SL = spring pre-load = 6 mm (0.24 in) B = 6 mm (0.24 in)	Hd = -17 mm (-0.67 in) E = 142 mm (5.6 in)	Hd = 10 mm (0.39 in) E = 154 mm (6.06 in)


The length E specifications are nominal values and may vary, due to the tolerances of the NPT threads.

Thermometer with thermowell according to DIN standard

The thermometer always has a thermowell.

 Thermowell, based on DIN 43772, Form 4F describes a flange, Form 4 the weld-in form as a process connection.

The thermometer can be configured as follows ²⁾



- 1 Version E: version with flange and removable extension neck
- 2 Version G: version for weld-in with QuickNeck
- 3 Version E: version with flange and extension neck with second process seal


Calculation of insert length IL

		Application Non-Ex/Ex ia/GP/IS	Application Ex d/XP
Version E with removable extension neck (feature 30: B, C, D)	$IL = U + T + E + Hd - B + GC + SL$ SL = spring pre-load = 2 mm (0.078 in) B = 6 mm (0.24 in) GC = 2 mm (0.078 in)	Hd = 11 mm (0.43 in) E = variable	Hd = 26 mm (1.02 in) E = variable
Version G with QuickNeck (feature 30: G)	$IL = U + T + E + Hd - B + GC + SL$ SL = spring pre-load = 2 mm (0.078 in) B = 6 mm (0.24 in) GC = 2 mm (0.078 in)	Hd = 11 mm (0.43 in) E = 74 mm (2.91 in)	Hd = 26 mm (1.02 in) E = 68 mm (2.67 in)
Version E with extension neck with second process seal (feature 30: H)	$IL = U + T + E + Hd - B + GC + SL$ SL = spring pre-load = 2 mm (0.078 in) B = 6 mm (0.24 in) GC = 2 mm (0.078 in)	Hd = 11 mm (0.43 in) E = 85 mm (3.35 in)	Hd = 26 mm (1.02 in) E = 76 mm (3 in)

Thermometer with thermowell as per NAMUR NE170

The thermometer always has a thermowell.

The thermometer can be configured as follows ²⁾



- 1 Version M without extension neck
- 2 Version M, extension neck with second process seal

A0051983


Calculation of insert length IL

		Application Non-Ex/Ex ia/GP/IS	Application Ex d/XP
Version M without extension neck (feature 30: A)	IL = U + T + Hd - B + SL Hd = 11 mm (0.43 in) B = 7 mm (0.28 in) SL = spring pre-load = 2 mm (0.08 in)	-	-
Version M, extension neck with second process seal (feature 30: H)	IL = U + T + E + Hd - B + SL B = 7 mm (0.28 in) SL = spring pre-load = 2 mm (0.08 in)	Hd = 11 mm (0.43 in) E = 56 mm (2.2 in)	Hd = 26 mm (1.02 in) E = 48 mm (1.9 in)

Thermometer with iTHERM TwistWell thermowell

The thermometer always has a thermowell.

The thermometer can be configured as follows²⁾



A0051987

- 1 Version T; iTHERM TwistWell, with flange and removable extension neck according to DIN standard
- 2 Version T; iTHERM TwistWell, with flange and QuickNeck
- 3 Version T; iTHERM TwistWell, with flange and extension neck with second process seal
- 4 Version T; iTHERM TwistWell, with flange and nipple connection
- 5 Version T; iTHERM TwistWell, with flange and nipple-union-nipple connection


Calculation of insert length IL

		Application Non-Ex/Ex ia/GP/IS	Application Ex d/XP
1: With flange and removable extension neck according to DIN standard	IL = U + T + E + Hd - B + GC + SL B = 6 mm (0.24 in) SL = spring pre-load = 2 mm (0.08 in) GC = 2 mm (0.078 in)	Hd = 11 mm (0.43 in) E = variable	Hd = 26 mm (1.02 in) E = variable
2: With flange and QuickNeck	IL = U + T + E + Hd - B + SL B = 6 mm (0.24 in) SL = spring pre-load = 6 mm (0.24 in)	Hd = -17 mm (-0.67 in) E = 101 mm (3.98 in)	Hd = 10 mm (0.39 in) E = 101 mm (3.98 in)

<p>3: With flange and extension neck with second process seal</p>	<p>$IL = U + T + E + Hd - B + SL$ $B = 6 \text{ mm (0.24 in)}$ $SL = \text{spring pre-load} = 6 \text{ mm (0.24 in)}$</p>	<p>$Hd = 11 \text{ mm (0.43 in)}$ $E = 147 \text{ mm (5.79 in)}$</p>	<p>$Hd = 26 \text{ mm (1.02 in)}$ $E = 158 \text{ mm (6.22 in)}$</p>
<p>4: With flange and nipple connection</p>	<p>$IL = U + T + E + Hd - B + SL$ $B = 6 \text{ mm (0.24 in)}$ $SL = \text{spring pre-load} = 6 \text{ mm (0.24 in)}$</p>	<p>$Hd = -17 \text{ mm (-0.67 in)}$ $E = 35 \text{ mm (1.38 in)}$</p>	<p>$Hd = 10 \text{ mm (0.39 in)}$ $E = 47 \text{ mm (1.85 in)}$</p>
<p>5: With flange and nipple-union-nipple connection</p>		<p>$Hd = -17 \text{ mm (-0.67 in)}$ $E = 142 \text{ mm (5.6 in)}$</p>	<p>$Hd = 10 \text{ mm (0.39 in)}$ $E = 158 \text{ mm (6.22 in)}$</p>

The length E specifications are nominal values and may vary, due to the tolerances of the NPT threads.

Forged thermowell






A0052379

To avoid having to use welded flanged process connections, you can opt for a forged thermowell. This offers the highest level of fatigue resistance in accordance with ASME PTC 19.3 TW. Opting for a forged thermowell means that welding seam checks and faults can be excluded. It can be used in extreme process environments.

This applies to the following thermowell versions: flanged, references acc. to ASME/Universal/DIN

Versions of flanged thermowells

Welded on both sides	Full penetration weld	Forged - not welded
 <p style="text-align: right; font-size: small;">A0052792</p>	 <p style="text-align: right; font-size: small;">A0052794</p>	 <p style="text-align: right; font-size: small;">A0052702</p>
<ul style="list-style-type: none"> ■ Suitable for most applications ■ Meets requirements with an optional cost-benefit ratio 	<ul style="list-style-type: none"> ■ Suitable for harsh application environments ■ Stronger welded connection ■ Higher costs 	<ul style="list-style-type: none"> ■ Suitable for harsh application environments ■ No welding ■ Cost-effective alternative to flange connection with full penetration welding

Weight 0.5 to 37 kg (1 to 82 lbs) for standard versions.

Materials Lagging and thermowell, insert, process connection

The temperatures for continuous operation specified in the following table are only intended as reference values for use of the various materials in air and without any significant mechanical load. The maximum operating temperatures can be reduced considerably in cases where abnormal conditions such as high mechanical load occur or in aggressive media.

Please note that the maximum temperature also always depends on the temperature sensor used!


Material name	Short form	Recommended max. temperature for continuous use in air	Properties
AISI 316/1.4401	X5CrNiMo 17-12-2	650 °C (1 202 °F) ¹⁾	<ul style="list-style-type: none"> ■ Austenitic, stainless steel ■ High corrosion resistance in general ■ Particularly high corrosion resistance in chlorinated and acidic, non-oxidizing atmospheres through the addition of molybdenum (e.g. phosphoric and sulfuric acids, acetic and tartaric acids with a low concentration)
AISI 316L/1.4404 1.4435	X2CrNiMo17-12-2 X2CrNiMo18-14-3	650 °C (1 202 °F) ¹⁾	<ul style="list-style-type: none"> ■ Austenitic, stainless steel ■ High corrosion resistance in general ■ Particularly high corrosion resistance in chlorinated and acidic, non-oxidizing atmospheres through the addition of molybdenum (e.g. phosphoric and sulfuric acids, acetic and tartaric acids with a low concentration) ■ Increased resistance to intergranular corrosion and pitting ■ Compared to 1.4404, 1.4435 has even higher corrosion resistance and a lower delta ferrite content

Material name	Short form	Recommended max. temperature for continuous use in air	Properties
AISI 316Ti/1.4571	X6CrNiMoTi17-12-2	700 °C (1292 °F) ¹⁾	<ul style="list-style-type: none"> ▪ Properties comparable with AISI316L ▪ Addition of titanium means increased resistance to intergranular corrosion even after welding ▪ Broad range of uses in the chemical, petrochemical and oil industries as well as in coal chemistry ▪ Can only be polished to a limited extent, titanium streaks can form
Alloy600/ 2.4816	NiCr15Fe	1 100 °C (2012 °F)	<ul style="list-style-type: none"> ▪ A nickel/chromium alloy with very good resistance to aggressive, oxidizing and reducing atmospheres, even at high temperatures ▪ Resistance to corrosion caused by chlorine gases and chlorinated media as well as many oxidizing mineral and organic acids, sea water etc. ▪ Corrosion from ultrapure water ▪ Not to be used in sulfur-containing atmospheres
AlloyC276/2.4819	NiMo16Cr15W	1 100 °C (2012 °F)	<ul style="list-style-type: none"> ▪ A nickel-based alloy with good resistance to oxidizing and reducing atmospheres, even at high temperatures ▪ Particularly resistant to chlorine gas and chloride as well as to many oxidizing mineral and organic acids
AISI 347/1.4550	X6CrNiNb18-10	900 °C (1 652 °F)	<ul style="list-style-type: none"> ▪ Austenitic, stainless steel ▪ Better intercrystalline corrosion resistance in oxidizing environments ▪ Good welding properties ▪ For high-temperature applications like furnaces
AISI 310/1.4841	X15CrNiSi25-20	1 100 °C (2012 °F)	<ul style="list-style-type: none"> ▪ Austenitic, stainless steel ▪ Generally good resistance to oxidizing and reducing atmospheres ▪ Due to the higher chromium content, good resistance to oxidizing aqueous solutions and neutral salts melting at higher temperatures ▪ Only low resistance to sulfur-containing gases
AISI A105/1.0460	C22.8	450 °C (842 °F)	<ul style="list-style-type: none"> ▪ Heat-resistant steel ▪ Resistant in nitrogen-containing atmospheres and atmospheres that are low in oxygen; not suitable for acids or other aggressive media ▪ Often used in steam generators, water and steam pipes, pressured vessels
AISI A182 F11/1.7335	13CrMo4-5	550 °C (1 022 °F)	<ul style="list-style-type: none"> ▪ Low alloy, heat-resistant steel with chromium and molybdenum additions ▪ Better corrosion resistance compared to non-alloy steels, not suitable for acids and other aggressive media ▪ Often used in steam generators, water and steam pipes, pressured vessels

Material name	Short form	Recommended max. temperature for continuous use in air	Properties
Titanium/3.7035	-	600 °C (1 112 °F)	<ul style="list-style-type: none"> ■ A light metal with very high corrosion resistance and strength values ■ Very good resistance to many oxidizing mineral and organic acids, saline solutions, sea water etc. ■ Prone to fast embrittlement at high temperatures through the absorption of oxygen, nitrogen and hydrogen ■ Compared to other metals, titanium reacts readily with many media (O₂, N₂, Cl₂, H₂) at higher temperatures and/or increased pressure ■ Can only be used in chlorine gas and chlorinated media at comparatively low temperatures (<400 °C)
1.5415	16Mo3	530 °C (986 °F)	<ul style="list-style-type: none"> ■ Alloyed creep-resistant steel ■ Particularly well suited as pipe material for boiler construction, super heater tube, superheated steam and collecting pipe, stove and line pipes, for heat exchangers and for the purposes of oil-refining industries
Duplex S32205	X2CrNi-MoN22-5-3	300 °C (572 °F)	<ul style="list-style-type: none"> ■ Austenitic ferritic steel with good mechanical properties ■ High resistance to general corrosion, pitting, chlorine-induced or transgranular stress corrosion ■ Comparatively good resistance to hydrogen-induced stress corrosion
1.7380	10CrMo9-10	580 °C (1 076 °F)	<ul style="list-style-type: none"> ■ Alloyed, heat-resistant steel ■ Particularly suitable for steam boilers, boiler parts, boiler drums, pressure vessels for apparatus constructions and similar purposes

- 1) Can be used to a limited extent up to 800 °C (1472 °F) for low mechanical loads and in non-corrosive media. Please contact your Endress+Hauser sales team for further information.

Thermowell/thermometer connections

Connection thread Metric female thread	Version	Thread length TL	Across flats	
 <p>1 Female thread</p>	M M24x1.5	14 mm (0.55 in)	30 mm (1.18 in)	The metric female thread is not designed as a process connection. This connection is only available for thermometers without a thermowell.

Connection thread Conical female thread	Version	Thread length TL	Across flats	
<p>1 Female thread</p>	NPT NPT ½"	8 mm (0.32 in)	22 mm (0.87 in)	The conical female thread is not designed as a process connection. This connection is only available for thermometers without a thermowell.

QuickNeck (upper half)	
	iTHERM QuickNeck - upper half - for installation in an existing thermowell with iTHERM QuickNeck.

Connection thread Male thread	Version	Thread length TL	Across flats	Max. process pressure	
<p>17 Cylindrical (left side) and conical (right side) version</p>	M	M14x1.5	12 mm (0.47 in)	22 mm (0.87 in)	Maximum static process pressure for threaded process connection: ¹⁾
		M20x1.5	14 mm (0.55 in)	27 mm (1.06 in)	
		M18x1.5	12 mm (0.47 in)	24 mm (0.95 in)	
	G ²⁾	G ½" DIN / BSP	15 mm (0.6 in)	27 mm (1.06 in)	400 bar (5 802 psi) at +400 °C (+752 °F)
NPT	NPT ½"	8 mm (0.32 in)	22 mm (0.87 in)		

- 1) Maximum pressure specifications only for the thread. The failure of the thread is calculated, taking the static pressure into consideration. The calculation is based on a fully tightened thread (TL = thread length)
- 2) DIN ISO 228 BSPP

Thermometer connection	Version Ge1		L_1	L_2	Standard/Class
<p>A0040912</p> <p>18 Female thread</p>	M	M14x1.5	17 mm (0.67 in)	20 mm (0.79 in)	ASME B1.13M/ISO 965-1 H6
		M20x1.5			
		M18x1.5			
	G ¹⁾	G ½" DIN / BSP			ISO 228-1 A
NPT	NPT ½"	ANSI B1.20.1			
<p>A0047327</p> <p>19 Adjustable male thread</p>					

1) DIN ISO 228 BSPP

Process connections Thread

Threaded process connection	Version	Thread length L_Gp	Standard	Max. process pressure	
<p>A0040916</p> <p>20 Cylindrical (left side) and conical (right side) version</p>	M	M20x1.5	ASME B1.13M ISO 965-1 g6	Maximum static process pressure for threaded process connection: ¹⁾ 400 bar (5802 psi) at +400 °C (+752 °F)	
		M27x2			16 mm (0.63 in)
		M33x2			18 mm (0.71 in)
	G	G ½"	15 mm (0.6 in)		ISO 228-1 A
	NPT	NPT ½"	20 mm (0.79 in)		ANSI B1.20.1
			L_Gp_e: 8 mm (0.32 in)		
NPT ¾"		20 mm (0.79 in)			
NPT 1"	NPT 1"	25 mm (0.98 in)	ANSI B1.20.1		
		L_Gp_e: 10 mm (0.39 in)			

1) Maximum pressure specifications only for the thread. The failure of the thread is calculated, taking the static pressure into consideration. The calculation is based on a fully tightened thread

WR size matrix for threaded thermowells (hexagonal lagging)

		Process connection size Gp (male thread)						
		M20x1.5	M27x2	M33x2	G 1/2"	NPT 1/2"	NPT 3/4"	NPT 1"
Thermometer connection, Ge1 (female thread)	M14x1.5	WR 27	WR 36	WR 41	WR 27	WR 24	WR 27	WR 27
	M18x1.5	WR 27	WR 36	WR 41	WR 27	WR 24	WR 27	WR 27
	M20x1.5	WR 27	WR 36	WR 41	WR 27	WR 24	WR 27	WR 27
	NPT 1/2"	WR 27	WR 36	WR 41	WR 27	WR 24	WR 27	WR 27
	G 1/2"	WR 27	WR 36	WR 41	WR 27	WR 24	WR 27	WR 27

A0040913

De1 size matrix for screw-in thermowells in mm (in)


		Process connection size Gp (male thread)						
		M20x1.5	M27x2	M33x2	G 1/2"	NPT 1/2"	NPT 3/4"	NPT 1"
Thermometer connection size Ge1 (female thread)	M14x1.5	26.7 (1.05)	33.4 (1.31)	40 (1.57)	26.7 (1.05)	26.7 (1.05)	26.7 (1.05)	33.4 (1.31)
	M18x1.5	26.7 (1.05)	33.4 (1.31)	40 (1.57)	26.7 (1.05)	26.7 (1.05)	26.7 (1.05)	33.4 (1.31)
	M20x1.5	26.7 (1.05)	33.4 (1.31)	40 (1.57)	26.7 (1.05)	26.7 (1.05)	26.7 (1.05)	33.4 (1.31)
	NPT 1/2"	26.7 (1.05)	33.4 (1.31)	40 (1.57)	26.7 (1.05)	26.7 (1.05)	26.7 (1.05)	33.4 (1.31)
	G 1/2"	26.7 (1.05)	33.4 (1.31)	40 (1.57)	26.7 (1.05)	26.7 (1.05)	26.7 (1.05)	33.4 (1.31)

A0040986


Wrench flats	WR 22	WR 27	WR 36	WR 22	WR 22	WR 22	WR 27
--------------	-------	-------	-------	-------	-------	-------	-------

Weld-in, socket weld

Weld-in version/socket weld



i Welding recommendation: distance between welding seam and end of thermowell should be at least 40 mm (1.57 in). To avoid thread deformations a dummy plug is recommended.












Flanges

i The flanges are supplied in stainless steel AISI 316L with material number 1.4404 or 1.4435. With regard to their stability-temperature property, the materials 1.4404 and 1.4435 are grouped together under 13E0 in DIN EN 1092-1 Tab.18 and under 023b in JIS B2220:2004 Tab. 5. The ASME flanges are grouped together under Tab. 2-2.2 in ASME B16.5-2013. Inches are converted into metric units (in - mm) using the factor 2.54. In the ASME standard, the metric data is rounded to 0 or 5.

Versions

- DIN flanges: German Standards Institute DIN 2527
- EN flanges: European standard DIN EN 1092-1:2002-06 and 2007
- ASME flanges: American Society of Mechanical Engineers ASME B16.5-2013
- JIS flanges: Japanese Industrial Standard B2220:2004
- HG/T flanges: Chinese Chemical Standard HG/T 20592-2009 and 20615-2009

Geometry of sealing surfaces

Flanges	Sealing surface	DIN 2526 ¹⁾		DIN EN 1092-1			ASME B16.5	
		Form	Rz (µm)	Form	Rz (µm)	Ra (µm)	Form	Ra (µm)
without raised face		A B	- 40 to 160	A ²⁾	12.5 to 50	3.2 to 12.5	Flat face (FF)	3.2 to 6.3 (AARH 125 to 250 µin)
with raised face		C D E	40 to 160 40 16	B1 ³⁾ B2	12.5 to 50 3.2 to 12.5	3.2 to 12.5 0.8 to 3.2	Raised face (RF)	
Tongue		F	-	C	3.2 to 12.5	0.8 to 3.2	Tongue (T)	3.2
Groove		N		D			Groove (G)	
Projection		V 13	-	E	12.5 to 50	3.2 to 12.5	Male (M)	3.2
Recess		R 13		F			Female (F)	
Projection		V 14	for O-rings	H	3.2 to 12.5	3.2 to 12.5	-	-
Recess		R 14		G			-	-
With ring-type joint		-	-	-	-	-	Ring-type joint (RTJ)	1.6

- 1) Contained in DIN 2527
- 2) Typically PN2.5 to PN40
- 3) Typically from PN63


Flanges according to the old DIN standard are compatible with the new DIN EN 1092-1 standard.
Change in pressure ratings: Old DIN standards PN64 → DIN EN 1092-1 PN63.

Height of raised face ¹⁾

Standard	Flanges	Height of raised face f	Tolerance
DIN EN 1092-1:2002-06	all types	2 (0.08)	0 -1 (-0.04)
DIN EN 1092-1:2007	≤ DN 32	3 (0.12)	0 -2 (-0.08)
	> DN 32 to DN 250	4 (0.16)	0 -3 (-0.12)
	> DN 250 to DN 500	5 (0.19)	0 -4 (-0.16)
	> DN 500	6.4 (0.25)	0.5 (0.02)
ASME B16.5 - 2013	≤ Class 300	1.6 (0.06)	±0.75 (±0.03)
	≥ Class 600	6.4 (0.25)	0.5 (0.02)
JIS B2220:2004	< DN 20	1.5 (0.06) 0	-
	> DN 20 to DN 50	2 (0.08) 0	
	> DN 50	3 (0.12) 0	

1) Dimensions in mm (in)

EN flanges (DIN EN 1092-1)



A0029176

21 Raised face B1

- L* Bore diameter
d Diameter of raised face
K Diameter of pitch circle
D Flange diameter
b Total flange thickness
f Height of raised face (generally 2 mm (0.08 in))

PN16 ¹⁾

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.50 (3.31)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.00 (4.41)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.50 (5.51)
50	165 (6.5)	18 (0.71)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	2.90 (6.39)
65	185 (7.28)	18 (0.71)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	3.50 (7.72)
80	200 (7.87)	20 (0.79)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	4.50 (9.92)
100	220 (8.66)	20 (0.79)	180 (7.09)	158 (6.22)	8xØ18 (0.71)	5.50 (12.13)
125	250 (9.84)	22 (0.87)	210 (8.27)	188 (7.40)	8xØ18 (0.71)	8.00 (17.64)
150	285 (11.2)	22 (0.87)	240 (9.45)	212 (8.35)	8xØ22 (0.87)	10.5 (23.15)
200	340 (13.4)	24 (0.94)	295 (11.6)	268 (10.6)	12xØ22 (0.87)	16.5 (36.38)

DN	D	b	K	d	L	approx. kg (lbs)
250	405 (15.9)	26 (1.02)	355 (14.0)	320 (12.6)	12xØ26 (1.02)	25.0 (55.13)
300	460 (18.1)	28 (1.10)	410 (16.1)	378 (14.9)	12xØ26 (1.02)	35.0 (77.18)

1) The dimensions in the following tables are in mm (in), unless otherwise specified

PN25

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.50 (3.31)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.00 (4.41)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.50 (5.51)
50	165 (6.5)	20 (0.79)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	3.00 (6.62)
65	185 (7.28)	22 (0.87)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	4.50 (9.92)
80	200 (7.87)	24 (0.94)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	5.50 (12.13)
100	235 (9.25)	24 (0.94)	190 (7.48)	162 (6.38)	8xØ22 (0.87)	7.50 (16.54)
125	270 (10.6)	26 (1.02)	220 (8.66)	188 (7.40)	8xØ26 (1.02)	11.0 (24.26)
150	300 (11.8)	28 (1.10)	250 (9.84)	218 (8.58)	8xØ26 (1.02)	14.5 (31.97)
200	360 (14.2)	30 (1.18)	310 (12.2)	278 (10.9)	12xØ26 (1.02)	22.5 (49.61)
250	425 (16.7)	32 (1.26)	370 (14.6)	335 (13.2)	12xØ30 (1.18)	33.5 (73.9)
300	485 (19.1)	34 (1.34)	430 (16.9)	395 (15.6)	16xØ30 (1.18)	46.5 (102.5)

PN40

DN	D	b	K	d	L	approx. kg (lbs)
15	95 (3.74)	16 (0.55)	65 (2.56)	45 (1.77)	4xØ14 (0.55)	0.81 (1.8)
25	115 (4.53)	18 (0.71)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.50 (3.31)
32	140 (5.51)	18 (0.71)	100 (3.94)	78 (3.07)	4xØ18 (0.71)	2.00 (4.41)
40	150 (5.91)	18 (0.71)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.50 (5.51)
50	165 (6.5)	20 (0.79)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	3.00 (6.62)
65	185 (7.28)	22 (0.87)	145 (5.71)	122 (4.80)	8xØ18 (0.71)	4.50 (9.92)
80	200 (7.87)	24 (0.94)	160 (6.30)	138 (5.43)	8xØ18 (0.71)	5.50 (12.13)
100	235 (9.25)	24 (0.94)	190 (7.48)	162 (6.38)	8xØ22 (0.87)	7.50 (16.54)
125	270 (10.6)	26 (1.02)	220 (8.66)	188 (7.40)	8xØ26 (1.02)	11.0 (24.26)
150	300 (11.8)	28 (1.10)	250 (9.84)	218 (8.58)	8xØ26 (1.02)	14.5 (31.97)
200	375 (14.8)	36 (1.42)	320 (12.6)	285 (11.2)	12xØ30 (1.18)	29.0 (63.95)
250	450 (17.7)	38 (1.50)	385 (15.2)	345 (13.6)	12xØ33 (1.30)	44.5 (98.12)
300	515 (20.3)	42 (1.65)	450 (17.7)	410 (16.1)	16xØ33 (1.30)	64.0 (141.1)

PN63


DN	D	b	K	d	L	approx. kg (lbs)
25	140 (5.51)	24 (0.94)	100 (3.94)	68 (2.68)	4xØ18 (0.71)	2.50 (5.51)
32	155 (6.10)	24 (0.94)	110 (4.33)	78 (3.07)	4xØ22 (0.87)	3.50 (7.72)
40	170 (6.69)	26 (1.02)	125 (4.92)	88 (3.46)	4xØ22 (0.87)	4.50 (9.92)
50	180 (7.09)	26 (1.02)	135 (5.31)	102 (4.02)	4xØ22 (0.87)	5.00 (11.03)
65	205 (8.07)	26 (1.02)	160 (6.30)	122 (4.80)	8xØ22 (0.87)	6.00 (13.23)

DN	D	b	K	d	L	approx. kg (lbs)
80	215 (8.46)	28 (1.10)	170 (6.69)	138 (5.43)	8xØ22 (0.87)	7.50 (16.54)
100	250 (9.84)	30 (1.18)	200 (7.87)	162 (6.38)	8xØ26 (1.02)	10.5 (23.15)
125	295 (11.6)	34 (1.34)	240 (9.45)	188 (7.40)	8xØ30 (1.18)	16.5 (36.38)
150	345 (13.6)	36 (1.42)	280 (11.0)	218 (8.58)	8xØ33 (1.30)	24.5 (54.02)
200	415 (16.3)	42 (1.65)	345 (13.6)	285 (11.2)	12xØ36 (1.42)	40.5 (89.3)
250	470 (18.5)	46 (1.81)	400 (15.7)	345 (13.6)	12xØ36 (1.42)	58.0 (127.9)
300	530 (20.9)	52 (2.05)	460 (18.1)	410 (16.1)	16xØ36 (1.42)	83.5 (184.1)

PN100

DN	D	b	K	d	L	approx. kg (lbs)
25	140 (5.51)	24 (0.94)	100 (3.94)	68 (2.68)	4xØ18 (0.71)	2.50 (5.51)
32	155 (6.10)	24 (0.94)	110 (4.33)	78 (3.07)	4xØ22 (0.87)	3.50 (7.72)
40	170 (6.69)	26 (1.02)	125 (4.92)	88 (3.46)	4xØ22 (0.87)	4.50 (9.92)
50	195 (7.68)	28 (1.10)	145 (5.71)	102 (4.02)	4xØ26 (1.02)	6.00 (13.23)
65	220 (8.66)	30 (1.18)	170 (6.69)	122 (4.80)	8xØ26 (1.02)	8.00 (17.64)
80	230 (9.06)	32 (1.26)	180 (7.09)	138 (5.43)	8xØ26 (1.02)	9.50 (20.95)
100	265 (10.4)	36 (1.42)	210 (8.27)	162 (6.38)	8xØ30 (1.18)	14.0 (30.87)
125	315 (12.4)	40 (1.57)	250 (9.84)	188 (7.40)	8xØ33 (1.30)	22.5 (49.61)
150	355 (14.0)	44 (1.73)	290 (11.4)	218 (8.58)	12xØ33 (1.30)	30.5 (67.25)
200	430 (16.9)	52 (2.05)	360 (14.2)	285 (11.2)	12xØ36 (1.42)	54.5 (120.2)
250	505 (19.9)	60 (2.36)	430 (16.9)	345 (13.6)	12xØ39 (1.54)	87.5 (192.9)
300	585 (23.0)	68 (2.68)	500 (19.7)	410 (16.1)	16xØ42 (1.65)	131.5 (289.9)

ASME flanges (ASME B16.5-2013)



A0029175

22 Raised face RF

L Bore diameter

d Diameter of raised face

K Diameter of pitch circle

D Flange diameter

b Total flange thickness

f Height of raised face, Class 150/300: 1.6 mm (0.06 in) or from Class 600: 6.4 mm (0.25 in)

Surface quality of sealing surface $R_a \leq 3.2$ to $6.3 \mu\text{m}$ (126 to 248 μin).Class 150¹⁾

DN	D	b	K	d	L	approx. kg (lbs)
1"	108.0 (4.25)	14.2 (0.56)	79.2 (3.12)	50.8 (2.00)	4xØ15.7 (0.62)	0.86 (1.9)
1¼"	117.3 (4.62)	15.7 (0.62)	88.9 (3.50)	63.5 (2.50)	4xØ15.7 (0.62)	1.17 (2.58)

DN	D	b	K	d	L	approx. kg (lbs)
1½"	127.0 (5.00)	17.5 (0.69)	98.6 (3.88)	73.2 (2.88)	4xØ15.7 (0.62)	1.53 (3.37)
2"	152.4 (6.00)	19.1 (0.75)	120.7 (4.75)	91.9 (3.62)	4xØ19.1 (0.75)	2.42 (5.34)
2½"	177.8 (7.00)	22.4 (0.88)	139.7 (5.50)	104.6 (4.12)	4xØ19.1 (0.75)	3.94 (8.69)
3"	190.5 (7.50)	23.9 (0.94)	152.4 (6.00)	127.0 (5.00)	4xØ19.1 (0.75)	4.93 (10.87)
3½"	215.9 (8.50)	23.9 (0.94)	177.8 (7.00)	139.7 (5.50)	8xØ19.1 (0.75)	6.17 (13.60)
4"	228.6 (9.00)	23.9 (0.94)	190.5 (7.50)	157.2 (6.19)	8xØ19.1 (0.75)	7.00 (15.44)
5"	254.0 (10.0)	23.9 (0.94)	215.9 (8.50)	185.7 (7.31)	8xØ22.4 (0.88)	8.63 (19.03)
6"	279.4 (11.0)	25.4 (1.00)	241.3 (9.50)	215.9 (8.50)	8xØ22.4 (0.88)	11.3 (24.92)
8"	342.9 (13.5)	28.4 (1.12)	298.5 (11.8)	269.7 (10.6)	8xØ22.4 (0.88)	19.6 (43.22)
10"	406.4 (16.0)	30.2 (1.19)	362.0 (14.3)	323.8 (12.7)	12xØ25.4 (1.00)	28.8 (63.50)

1) The dimensions in the following tables are in mm (in), unless otherwise specified

Class 300

DN	D	b	K	d	L	approx. kg (lbs)
1"	124.0 (4.88)	17.5 (0.69)	88.9 (3.50)	50.8 (2.00)	4xØ19.1 (0.75)	1.39 (3.06)
1¼"	133.4 (5.25)	19.1 (0.75)	98.6 (3.88)	63.5 (2.50)	4xØ19.1 (0.75)	1.79 (3.95)
1½"	155.4 (6.12)	20.6 (0.81)	114.3 (4.50)	73.2 (2.88)	4xØ22.4 (0.88)	2.66 (5.87)
2"	165.1 (6.50)	22.4 (0.88)	127.0 (5.00)	91.9 (3.62)	8xØ19.1 (0.75)	3.18 (7.01)
2½"	190.5 (7.50)	25.4 (1.00)	149.4 (5.88)	104.6 (4.12)	8xØ22.4 (0.88)	4.85 (10.69)
3"	209.5 (8.25)	28.4 (1.12)	168.1 (6.62)	127.0 (5.00)	8xØ22.4 (0.88)	6.81 (15.02)
3½"	228.6 (9.00)	30.2 (1.19)	184.2 (7.25)	139.7 (5.50)	8xØ22.4 (0.88)	8.71 (19.21)
4"	254.0 (10.0)	31.8 (1.25)	200.2 (7.88)	157.2 (6.19)	8xØ22.4 (0.88)	11.5 (25.36)
5"	279.4 (11.0)	35.1 (1.38)	235.0 (9.25)	185.7 (7.31)	8xØ22.4 (0.88)	15.6 (34.4)
6"	317.5 (12.5)	36.6 (1.44)	269.7 (10.6)	215.9 (8.50)	12xØ22.4 (0.88)	20.9 (46.08)
8"	381.0 (15.0)	41.1 (1.62)	330.2 (13.0)	269.7 (10.6)	12xØ25.4 (1.00)	34.3 (75.63)
10"	444.5 (17.5)	47.8 (1.88)	387.4 (15.3)	323.8 (12.7)	16xØ28.4 (1.12)	53.3 (117.5)

Class 600

DN	D	b	K	d	L	approx. kg (lbs)
1"	124.0 (4.88)	17.5 (0.69)	88.9 (3.50)	50.8 (2.00)	4xØ19.1 (0.75)	1.60 (3.53)
1¼"	133.4 (5.25)	20.6 (0.81)	98.6 (3.88)	63.5 (2.50)	4xØ19.1 (0.75)	2.23 (4.92)
1½"	155.4 (6.12)	22.4 (0.88)	114.3 (4.50)	73.2 (2.88)	4xØ22.4 (0.88)	3.25 (7.17)
2"	165.1 (6.50)	25.4 (1.00)	127.0 (5.00)	91.9 (3.62)	8xØ19.1 (0.75)	4.15 (9.15)
2½"	190.5 (7.50)	28.4 (1.12)	149.4 (5.88)	104.6 (4.12)	8xØ22.4 (0.88)	6.13 (13.52)
3"	209.5 (8.25)	31.8 (1.25)	168.1 (6.62)	127.0 (5.00)	8xØ22.4 (0.88)	8.44 (18.61)
3½"	228.6 (9.00)	35.1 (1.38)	184.2 (7.25)	139.7 (5.50)	8xØ25.4 (1.00)	11.0 (24.26)
4"	273.1 (10.8)	38.1 (1.50)	215.9 (8.50)	157.2 (6.19)	8xØ25.4 (1.00)	17.3 (38.15)
5"	330.2 (13.0)	44.5 (1.75)	266.7 (10.5)	185.7 (7.31)	8xØ28.4 (1.12)	29.4 (64.83)
6"	355.6 (14.0)	47.8 (1.88)	292.1 (11.5)	215.9 (8.50)	12xØ28.4 (1.12)	36.1 (79.6)
8"	419.1 (16.5)	55.6 (2.19)	349.3 (13.8)	269.7 (10.6)	12xØ31.8 (1.25)	58.9 (129.9)
10"	508.0 (20.0)	63.5 (2.50)	431.8 (17.0)	323.8 (12.7)	16xØ35.1 (1.38)	97.5 (214.9)


Class 900

DN	D	b	K	d	L	approx. kg (lbs)
1"	149.4 (5.88)	28.4 (1.12)	101.6 (4.0)	50.8 (2.00)	4xØ25.4 (1.00)	3.57 (7.87)
1¼"	158.8 (6.25)	28.4 (1.12)	111.3 (4.38)	63.5 (2.50)	4xØ25.4 (1.00)	4.14 (9.13)
1½"	177.8 (7.0)	31.8 (1.25)	124.0 (4.88)	73.2 (2.88)	4xØ28.4 (1.12)	5.75 (12.68)
2"	215.9 (8.50)	38.1 (1.50)	165.1 (6.50)	91.9 (3.62)	8xØ25.4 (1.00)	10.1 (22.27)
2½"	244.4 (9.62)	41.1 (1.62)	190.5 (7.50)	104.6 (4.12)	8xØ28.4 (1.12)	14.0 (30.87)
3"	241.3 (9.50)	38.1 (1.50)	190.5 (7.50)	127.0 (5.00)	8xØ25.4 (1.00)	13.1 (28.89)
4"	292.1 (11.50)	44.5 (1.75)	235.0 (9.25)	157.2 (6.19)	8xØ31.8 (1.25)	26.9 (59.31)
5"	349.3 (13.8)	50.8 (2.0)	279.4 (11.0)	185.7 (7.31)	8xØ35.1 (1.38)	36.5 (80.48)
6"	381.0 (15.0)	55.6 (2.19)	317.5 (12.5)	215.9 (8.50)	12xØ31.8 (1.25)	47.4 (104.5)
8"	469.9 (18.5)	63.5 (2.50)	393.7 (15.5)	269.7 (10.6)	12xØ38.1 (1.50)	82.5 (181.9)
10"	546.1 (21.50)	69.9 (2.75)	469.0 (18.5)	323.8 (12.7)	16xØ38.1 (1.50)	122 (269.0)

Class 1500

DN	D	b	K	d	L	approx. kg (lbs)
1"	149.4 (5.88)	28.4 (1.12)	101.6 (4.0)	50.8 (2.00)	4xØ25.4 (1.00)	3.57 (7.87)
1¼"	158.8 (6.25)	28.4 (1.12)	111.3 (4.38)	63.5 (2.50)	4xØ25.4 (1.00)	4.14 (9.13)
1½"	177.8 (7.0)	31.8 (1.25)	124.0 (4.88)	73.2 (2.88)	4xØ28.4 (1.12)	5.75 (12.68)
2"	215.9 (8.50)	38.1 (1.50)	165.1 (6.50)	91.9 (3.62)	8xØ25.4 (1.00)	10.1 (22.27)
2½"	244.4 (9.62)	41.1 (1.62)	190.5 (7.50)	104.6 (4.12)	8xØ28.4 (1.12)	14.0 (30.87)
3"	266.7 (10.5)	47.8 (1.88)	203.2 (8.00)	127.0 (5.00)	8xØ31.8 (1.25)	19.1 (42.12)
4"	311.2 (12.3)	53.8 (2.12)	241.3 (9.50)	157.2 (6.19)	8xØ35.1 (1.38)	29.9 (65.93)
5"	374.7 (14.8)	73.2 (2.88)	292.1 (11.5)	185.7 (7.31)	8xØ41.1 (1.62)	58.4 (128.8)
6"	393.7 (15.50)	82.6 (3.25)	317.5 (12.5)	215.9 (8.50)	12xØ38.1 (1.50)	71.8 (158.3)
8"	482.6 (19.0)	91.9 (3.62)	393.7 (15.5)	269.7 (10.6)	12xØ44.5 (1.75)	122 (269.0)
10"	584.2 (23.0)	108.0 (4.25)	482.6 (19.0)	323.8 (12.7)	12xØ50.8 (2.00)	210 (463.0)

HG/T flanges (HG/T 20592-2009)



A0029176

 23 Raised face

- L* Bore diameter
d Diameter of raised face
K Diameter of pitch circle
D Flange diameter
b Total flange thickness
f Height of raised face (generally 2 mm (0.08 in))


PN40

DN	D	b	K	d	L	approx. kg (lbs)
25	115 (4.53)	16 (0.63)	85 (3.35)	68 (2.68)	4xØ14 (0.55)	1.50 (3.31)
40	150 (5.91)	16 (0.63)	110 (4.33)	88 (3.46)	4xØ18 (0.71)	2.50 (5.51)
50	165 (6.5)	18 (0.71)	125 (4.92)	102 (4.02)	4xØ18 (0.71)	3.00 (6.62)

PN63

DN	D	b	K	d	L	approx. kg (lbs)
50	180 (7.09)	24 (0.95)	135 (5.31)	102 (4.02)	4xØ22 (0.87)	5.00 (11.03)

HG/T flanges (HG/T 20615-2009)



A0029175

24 Raised face

L Bore diameter

d Diameter of raised face

K Diameter of pitch circle

D Flange diameter

b Total flange thickness

f Height of raised face, Class 150/300: 2 mm (0.08 in) or from Class 600: 7 mm (0.28 in)

Surface quality of sealing surface $R_a \leq 3.2$ to $6.3 \mu\text{m}$ (126 to 248 μin).

Class 150¹⁾

DN	D	b	K	d	L	approx. kg (lbs)
1"	110.0 (4.33)	12.7 (0.5)	79.4 (3.13)	50.8 (2.00)	4xØ16 (0.63)	0.86 (1.9)
1½"	125.0 (4.92)	15.9 (0.63)	98.4 (3.87)	73.0 (2.87)	4xØ16 (0.63)	1.53 (3.37)
2"	150 (5.91)	17.5 (0.69)	120.7 (4.75)	92.1 (3.63)	4xØ18 (0.71)	2.42 (5.34)

1) The dimensions in the following tables are in mm (in), unless otherwise specified

Class 300


DN	D	b	K	d	L	approx. kg (lbs)
1"	125.0 (4.92)	15.9 (0.63)	88.9 (3.50)	50.8 (2.00)	4xØ18 (0.71)	1.39 (3.06)
1½"	155 (6.10)	19.1 (0.75)	114.3 (4.50)	73 (2.87)	4xØ22 (0.87)	2.66 (5.87)
2"	165 (6.50)	20.7 (0.82)	127.0 (5.00)	92.1 (3.63)	8xØ18 (0.71)	3.18 (7.01)

Class 600

DN	D	b	K	d	L	approx. kg (lbs)
2"	165 (6.50)	25.4 (1.00)	127.0 (5.00)	92.1 (3.63)	8xØ18 (0.71)	4.15 (9.15)

Thermowell material, nickel-based, with flange


If the thermowell materials Alloy600 and Alloy C276 are combined with a flange process connection, only the raised face and not the complete flange is made of the alloy for cost reasons. This is welded onto a flange with the parent material 316L. Identified in the order code by the material designation Alloy600 > 316L or Alloy C276 > 316L.



A0043523

- 1 Raised face
- 2 Weld

Geometry of parts in contact with medium



A0051990

- 1 Straight (complete length U)
- 2 Tapered (complete length U)
- 3 Tapered (over length C1)
- 4 Stepped, Re1 = 63.5 mm (2.5 in)
- 5 Stepped bore diameter (D1/Di2)

Inserts

Depending on the configuration, iTHERM TS111 or TS211 inserts with different RTD and TC sensors are available for the thermometer. For information on the assignment of inserts to certain extension neck versions, see the "Extension neck" section.

Sensor	Standard thin-film	iTHERM StrongSens	iTHERM QuickSens ¹⁾	Wire wound	
Sensor design; connection method	1x Pt100, 3- or 4-wire, mineral insulated	1x Pt100, 3- or 4-wire, mineral insulated	1x Pt100, 3- or 4-wire <ul style="list-style-type: none"> ■ Ø6 mm (0.24 in), mineral insulated ■ Ø3 mm (0.12 in), Teflon insulated 	1x Pt100, 3- or 4-wire, mineral insulated	2x Pt100, 3-wire, mineral insulated
Vibration resistance of the insert tip	< 3g	Enhanced vibration resistance > 60g	<ul style="list-style-type: none"> ■ Ø3 mm (0.12 in) < 3g ■ Ø6 mm (0.24 in) > 60g 	< 3g	

Measuring range	-50 to +400 °C (-58 to +752 °F)	-50 to +500 °C (-58 to +932 °F)	-50 to +200 °C (-58 to +392 °F)	-200 to +600 °C (-328 to +1 112 °F)
Diameter	3 mm (0.12 in), 6 mm (0.24 in)	6 mm (0.24 in)	3 mm (0.12 in), 6 mm (0.24 in)	

1) Recommended for immersion lengths U < 70 mm (2.76 in)

TC thermocouples	Type K	Type J	Type N
Sensor design	Mineral insulated, Alloy600 sheathed cable	Mineral insulated, stainless steel sheathed cable	Mineral insulated, Alloy TD sheathed cable
Vibration resistance of the insert tip	< 3g		
Measuring range	-40 to +1 100 °C (-40 to +2 012 °F)	-40 to +750 °C (-40 to +1 382 °F)	-40 to +1 100 °C (-40 to +2 012 °F)
Connection type	Grounded or ungrounded		
Temperature-sensitive length	Insert length		
Diameter	3 mm (0.12 in), 6 mm (0.24 in)		

The iTHERM inserts are available as a spare part. The insertion length (IL) depends on the immersion length of the thermowell (U), the length of the extension neck (E), the bottom thickness (B), the length of the lagging (L) and the variable length (X). The insertion length (IL) must be taken into consideration when replacing the unit. Formulas for calculating IL in the **Mechanical construction** section.



For more information on the deployed insert iTHERM TS111 and TS211 with enhanced vibration resistance and fast-response sensor, see the Technical Information (TI01014T and TI01411T).



Spare parts currently available for your product can be found online at: http://www.products.endress.com/spareparts_consumables. Choose the corresponding product root. Always quote the serial number of the device when ordering spare parts! The insertion length IL is automatically calculated using the serial number.

Surface roughness

Specifications for surfaces in contact with medium

Standard surface	$R_a \leq 1.6 \mu\text{m}$ (63 μin)
Finely honed surface, buffed	$R_a \leq 0.76 \mu\text{m}$ (30 μin)


Terminal heads


All terminal heads have an internal shape and size in accordance with DIN EN 50446, flat face and a thermometer connection with a M24x1.5 or 1/2" NPT thread. All dimensions in mm (in). The sample cable glands in the diagrams correspond to M20x1.5 connections with non-Ex polyamide cable glands. Specifications without head transmitter installed. For ambient temperatures with head transmitter installed, see the "Environment" section.


As a special feature, Endress+Hauser offers terminal heads with optimized terminal accessibility for easy installation and maintenance.



IP 68 = 1.83 m (6 ft), 24 h, with cable gland without cable (with plug), type 6P as per NEMA250-2003


TA30A	Specification
	<ul style="list-style-type: none"> ▪ Degree of protection: <ul style="list-style-type: none"> ▪ IP66/68 (NEMA Type 4x incl.) ▪ For ATEX: IP66/67 ▪ Temperature: -50 to +150 °C (-58 to +302 °F) without cable gland ▪ Material: aluminum, polyester powder coated Seals: silicone ▪ Cable entry thread: G ½", ½" NPT and M20x1.5; ▪ Protective fitting connection: M24x1.5 ▪ Head color: blue, RAL 5012 ▪ Cap color: gray, RAL 7035 ▪ Weight: 330 g (11.64 oz) ▪ Ground terminal, internal and external ▪ Available with sensors with 3-A® symbol




TA30A with display window in cover	Specification
	<ul style="list-style-type: none"> ▪ Degree of protection: <ul style="list-style-type: none"> ▪ IP66/68 (NEMA Type 4x incl.) ▪ For ATEX: IP66/67 ▪ Temperature: -50 to +150 °C (-58 to +302 °F) without cable gland ▪ Material: aluminum, polyester powder coated Seals: silicone ▪ Cable entry thread: G ½", ½" NPT and M20x1.5 ▪ Protective fitting connection: M24x1.5 ▪ Color of head: blue, RAL 5012 Color of cap: gray, RAL 7035 ▪ Weight: 420 g (14.81 oz) ▪ Display window: single-pane safety glass according to DIN 8902 ▪ Display window in cover for head transmitter with TID10 display ▪ Ground terminal, internal and external ▪ Available with sensors with 3-A® symbol


TA30D	Specification
	<ul style="list-style-type: none"> ▪ Degree of protection: <ul style="list-style-type: none"> ▪ IP66/68 (NEMA Type 4x incl.) ▪ For ATEX: IP66/67 ▪ Temperature: -50 to +150 °C (-58 to +302 °F) without cable gland ▪ Material: aluminum, polyester powder coated Seals: silicone ▪ Cable entry thread: G ½", ½" NPT and M20x1.5 ▪ Protective fitting connection: M24x1.5 ▪ Two head transmitters can be mounted. In the standard configuration one transmitter is mounted in the terminal head cover and an additional terminal block is installed directly on the insert. ▪ Head color: blue, RAL 5012 ▪ Cap color: gray, RAL 7035 ▪ Weight: 390 g (13.75 oz) ▪ Ground terminal, internal and external ▪ Available with sensors with 3-A® symbol


TA30P	Specification
	<ul style="list-style-type: none"> ■ Degree of protection: IP65 ■ Max. temperature: -40 to +120 °C (-40 to +248 °F) ■ Material: polyamide (PA12), antistatic ■ Seals: silicone ■ Threaded cable entry: M20x1.5 ■ Protective fitting connection: M24x1.5 ■ Two head transmitters can be mounted. In the standard configuration one transmitter is mounted in the terminal head cover and an additional terminal block is installed directly on the insert. ■ Head and cap color: black ■ Weight: 135 g (4.8 oz) ■ Type of protection: intrinsic safety (G Ex ia) ■ Ground terminal: only internal via auxiliary terminal ■ Available with sensors with 3-A® symbol


TA30R (optionally with display window in cover)	Specification
	<ul style="list-style-type: none"> ■ Degree of protection - standard version: IP69K (NEMA Type 4x encl.) ■ Degree of protection - version with display window: IP66/68 (NEMA Type 4x encl.) ■ Temperature: -50 to +130 °C (-58 to +266 °F) without cable gland ■ Material: stainless steel 316L, abrasive-blasted or polished ■ Seals: silicone, optional EPDM for applications free from paint-wetting impairment substances ■ Display window: polycarbonate (PC) ■ Cable entry thread ½" NPT and M20x1.5 ■ Weight <ul style="list-style-type: none"> ■ Standard version: 360 g (12.7 oz) ■ Version with display window: 460 g (16.23 oz) ■ Display window in cover optionally for head transmitter with display TID10 ■ Protection armature connection: M24x1.5 or ½" NPT ■ Ground terminal: internal as standard ■ Available with 3-A marked sensors ■ Not allowed for Class II and III applications


TA30R (high version for two transmitters)	Specification
 <p style="text-align: right; font-size: small;">A0034644</p>	<ul style="list-style-type: none"> ▪ Degree of protection: IP69K (NEMA Type 4x encl.) ▪ Temperature: -50 to +130 °C (-58 to +266 °F) without cable gland ▪ Material: stainless steel 316L, abrasive-blasted or polished ▪ Seals: EPDM ▪ Cable entry thread ½" NPT and M20x1.5 ▪ Weight: 460 g (16.23 oz) ▪ For two head transmitter ▪ Protection armature connection: M24x1.5 or ½" NPT ▪ Ground terminal: internal in standard version ▪ Not allowed for Class II and III applications ▪ Available with 3-A marked sensors


TA30H with display window in cover	Specification
 <p data-bbox="496 1458 1078 1514">  25 Terminal head used as field housing with display frontal mounted </p> <p data-bbox="496 1525 1078 1666"> 1 One cable entry is used as sensor input channel with an insert, TS211 for example 2 Cable entry used for wiring 3 The bottom entry into the housing is not available for the field housing version </p>	<ul style="list-style-type: none"> <li data-bbox="1078 275 1540 360">■ Flameproof (XP) version, explosion-protected, captive screw cap, available with one or two cable entries <li data-bbox="1078 360 1540 445">■ Degree of protection: IP 66/68, NEMA Type 4x encl. Ex-version: IP 66/67 <li data-bbox="1078 445 1540 548">■ Temperature: -50 to +150 °C (-58 to +302 °F) for rubber seal without cable gland (observe max. permitted temperature of cable gland!) <li data-bbox="1078 548 1540 651">■ Material: <ul style="list-style-type: none"> ■ Aluminum; polyester powder coated ■ Stainless steel 316L without coating ■ Klüber Syntheso Glep 1 dry-film lubricant <li data-bbox="1078 651 1540 707">■ Display window: single-pane safety glass according to DIN 8902 <li data-bbox="1078 707 1540 741">■ Thread: ½" NPT, ¾" NPT, M20x1.5, G½" <li data-bbox="1078 741 1540 797">■ Extension neck/thermowell connection: M20x1.5 or ½" NPT <li data-bbox="1078 797 1540 831">■ Color of aluminum head: blue, RAL 5012 <li data-bbox="1078 831 1540 864">■ Color of aluminum cap: gray, RAL 7035 <li data-bbox="1078 864 1540 920">■ Weight: <ul style="list-style-type: none"> ■ Aluminum approx. 860 g (30.33 oz) ■ Stainless steel approx. 2 900 g (102.3 oz) <li data-bbox="1078 920 1540 976">■ Head transmitter optionally available with TID10 display <p data-bbox="1078 987 1540 1122">  If the housing cover is unscrewed: Before tightening, clean the thread in the cover and housing base and lubricate if necessary (Recommended lubricant: Klüber Syntheso Glep 1) </p>

TA30H	Specification
 <p>A0009832</p>	<ul style="list-style-type: none"> ▪ Flameproof (XP) version, explosion-protected, captive screw cap, available with one or two cable entries ▪ Degree of protection: IP 66/68, NEMA Type 4x encl. Ex-version: IP 66/67 ▪ Temperature: -50 to +150 °C (-58 to +302 °F) for rubber seal without cable gland (observe max. permitted temperature of cable gland!) ▪ Material: <ul style="list-style-type: none"> ▪ Aluminum with polyester powder coating ▪ Stainless steel 316L without coating ▪ Klüber Syntheso Glep 1 dry-film lubricant ▪ Thread: ½" NPT, ¾" NPT, M20x1.5, G½" ▪ Extension neck/thermowell connection: M20x1.5 or ½" NPT ▪ Color of aluminum head: blue, RAL 5012 ▪ Color of aluminum cap: gray, RAL 7035 ▪ Weight: <ul style="list-style-type: none"> ▪ Aluminum: approx. 640 g (22.6 oz) ▪ Stainless steel: approx. 2 400 g (84.7 oz) <p>i If the housing cover is unscrewed: Before tightening, clean the thread in the cover and housing base and lubricate if necessary (Recommended lubricant: Klüber Syntheso Glep 1)</p>

TA30EB	Specification
 <p>A0038414</p>	<ul style="list-style-type: none"> ▪ Screw cap ▪ Degree of protection: IP 66/68, NEMA 4x ▪ Temperature: -50 to +150 °C (-58 to +302 °F) ▪ Material: aluminum; polyester powder coating; Klüber Syntheso Glep 1 dry-film lubricant ▪ Thread: M20x1.5 ▪ Extension neck/thermowell connection: NPT ½" ▪ Color of head: blue, RAL 5012 ▪ Color of cap: gray, RAL 7035 ▪ Weight: approx. 400 g (14.11 oz) ▪ Ground terminal: internal and external <p>i If the housing cover is unscrewed: Before tightening, clean the thread in the cover and housing base and lubricate if necessary (Recommended lubricant: Klüber Syntheso Glep 1)</p>

TA30EB with display window in cover	Specification
 <p>A0038428</p>	<ul style="list-style-type: none"> ▪ Screw cap ▪ Degree of protection: IP 66/68, NEMA 4x Ex-version: IP 66/68 ▪ Temperature: -50 to +150 °C (-58 to +302 °F) for rubber seal without cable gland (observe max. permitted temperature of cable gland!) ▪ Material: aluminum; polyester powder coating; Klüber Syntheso Glep 1 dry-film lubricant ▪ Display window: single-pane safety glass according to DIN 8902 ▪ Thread: ½" NPT, ¾" NPT, M20x1.5, G½" ▪ Extension neck/thermowell connection: ½" NPT ▪ Color of head: blue, RAL 5012 ▪ Color of cap: gray, RAL 7035 ▪ Weight: approx. 400 g (14.11 oz) <p>i If the housing cover is unscrewed: Before tightening, clean the thread in the cover and housing base and lubricate if necessary (Recommended lubricant: Klüber Syntheso Glep 1)</p>

Temperature field transmitter iTEMP TMT162	Specification
 <p>A0024608</p> <p>* Dimensions without display = 112 mm (4.41 in)</p>	<ul style="list-style-type: none"> ▪ Separate electronics compartment and connection compartment ▪ Protection class: IP67, NEMA type 4x ▪ Material: Die-cast aluminum housing AlSi10Mg with powder coating on polyester base or stainless steel 316L ▪ Display rotatable in 90° increments ▪ Cable entry: 2x ½" NPT ▪ Brilliant backlit display with ease of visibility in bright sunshine or pitch darkness ▪ Gold plated terminals to avoid corrosion and additional measurement errors ▪ SIL certification as per IEC 61508:2010 (HART-protocol) ▪ Integrated surge arrester to prevent damage from overvoltage, optional

Temperature field transmitter iTEMP TMT142B	Specification
	<ul style="list-style-type: none"> ■ Protection class: IP66/67, NEMA type 4x ■ Material: Die-cast aluminum housing AlSi10Mg with powder coating on polyester base or stainless steel 316L ■ Display rotatable in 90° increments ■ Integrated Bluetooth® interface for wireless measured value display and parameter configuration, optional ■ Bright backlit display with ease of visibility in bright sunshine or pitch darkness ■ Gold plated terminals to avoid corrosion and additional measurement errors ■ Integrated overvoltage protection for the prevention of damage from overvoltage, optional

Cable glands and connectors ¹⁾

Type	Suitable for cable entry	Degree of protection	Temperature range	Suitable cable diameter
Cable gland, polyamide blue (indication of Ex-i circuit)	½" NPT	IP68	-30 to +95 °C (-22 to +203 °F)	7 to 12 mm (0.27 to 0.47 in)
Cable gland, polyamide	½" NPT, ¾" NPT, M20x1.5 (optionally 2x cable entry)	IP68	-40 to +100 °C (-40 to +212 °F)	5 to 9 mm (0.19 to 0.35 in)
	½" NPT, M20x1.5 (optionally 2x cable entry)	IP69K	-20 to +95 °C (-4 to +203 °F)	
Cable gland for dust ignition-proof area, polyamide	½" NPT, M20x1.5	IP68	-20 to +95 °C (-4 to +203 °F)	
Cable gland for dust ignition-proof area, brass	M20x1.5	IP68 (NEMA Type 4x)	-20 to +130 °C (-4 to +266 °F)	
M12 plug, 4-pin, 316 (PROFIBUS® PA, Ethernet-APL, IO-Link®)	½" NPT, M20x1.5	IP67	-40 to +105 °C (-40 to +221 °F)	

Type	Suitable for cable entry	Degree of protection	Temperature range	Suitable cable diameter
M12 plug, 8-pin, 316	M20x1.5	IP67	-30 to +90 °C (-22 to +194 °F)	-
7/8" plug, 4-pin, 316 (FOUNDATION™ Fieldbus, PROFIBUS® PA)	½" NPT, M20x1.5	IP67	-40 to +105 °C (-40 to +221 °F)	-

1) Depending on product and configuration

 For explosion proof thermometers no cable glands are assembled.


Extension neck

The extension neck is the part between the thermowell and the terminal head. The term E is used to describe the length of the removable extension neck.

Different versions of the removable extension neck are possible.

Removable extension neck according DIN 43772


The removable extension neck according to DIN has a threaded connection on both sides. If the thermometer has a thermowell, the connection is designed according to the 'Pre-defined versions' section. If the thermometer does not have a thermowell, and is intended for installation in a separate thermowell, the thread for the thermowell connection can be selected (*feature 50: process/thermowell connection*)



- 1 Removable extension neck - thermometer without thermowell, insert TS111
 2 Removable extension neck - thermometer with thermowell, insert TS111

Removable extension neck as QuickNeck

If the thermometer does not have a thermowell, select the QuickNeck (upper half) or QuickNeck option (*feature 30: Thermometer structure*). The length of the removable extension neck is predetermined by the chosen design here.




A0052002

- 1 iTHERM QuickNeck - upper half - for installation in an existing thermowell with iTHERM QuickNeck according to DIN standard
- 2 iTHERM QuickNeck - upper half - for installation in an existing thermowell with iTHERM QuickNeck according to ASME standard
- 3 iTHERM QuickNeck complete, for installation in an existing thermowell according to DIN standard
- 4 iTHERM QuickNeck complete, for installation in an existing thermowell according to ASME standard
- 5 iTHERM QuickNeck installed in thermowell according to DIN standard
- 6 iTHERM QuickNeck installed in thermowell according to ASME standard

Removable extension neck as 'second process seal'

The removable extension neck can be designed as a second process seal. The length of the removable extension neck is predetermined by the chosen design here.




A0052026

- 1 Extension neck with second process seal without a thermowell
- 2 Extension neck with second process seal with a thermowell according to DIN standard
- 3 Extension neck with second process seal with a thermowell according to ASME standard

Removable extension neck as nipple connection


- The removable extension neck can be designed as a nipple connection. In this case, the connection is always an NPT 1/2" thread. The nipple directly on the terminal head is part of the TS211 insert in this case. The length of the nipple is not variable. It is 35 mm (1.38 in) as the standard version and 47 mm (1.85 in) as a lamination nipple version for Ex d applications.
- For the nipple-union connection, an NPT 1/2" female thread is used for the connection to the thermowell. The nipple directly on the terminal head is part of the TS211 insert in this case. The overall length is not variable. It is 93 mm (3.66 in) as the standard version and 105 mm (4.13 in) as a lamination nipple version for Ex d applications.
- In the case of the nipple-union-nipple connection, the nipple directly on the terminal head is part of the TS211 insert. The overall length is not variable. It is 142 mm (5.6 in) as the standard version and 154 mm (6.06 in) as the version for Ex d applications. In the case of this connection, the length of the second nipple can be configured if required.



A0045381

- 1 Extension neck type N (nipple) NPT 1/2"
- 2 Extension neck type NU (nipple-union) NPT 1/2" female thread
- 3 Extension neck type NUN (nipple-union-nipple) NPT 1/2", the length of the lower nipple can be configured

As illustrated in the following diagram, the length of the extension neck can influence the temperature in the terminal head. This temperature must remain within the limit values defined in the "Operating conditions" section.



26 Heating of the terminal head as a function of the process temperature. Temperature in terminal head = ambient temperature 20 °C (68 °F) + ΔT

The diagram can be used to calculate the transmitter temperature.

Example: At a process temperature of 220 °C (428 °F) and with a lagging length of 100 mm (3.94 in), the heat conduction is 40 K (72 °F). The transmitter temperature is therefore 40 K (72 °F) plus the ambient temperature, e.g. 25 °C (77 °F): 40 K (72 °F) + 25 °C (77 °F) = 65 °C (149 °F).


Result: The temperature of the transmitter is OK; the length of the lagging is sufficient.

Extension neck with second process seal

A special version of the extension neck is available with a second process seal, which can be placed as an optional component between the thermowell and the terminal head. In the event of a thermowell failure, no process medium will enter the terminal head or the wiring circuit. The process medium is held in the thermowell. A pressure switch emits a signal if the pressure in the component with the second process seal increases in order to alert the maintenance personnel to a dangerous situation. Measurement can continue for a short transition period, depending on the pressure, temperature and process medium, until the thermowell is replaced.

Transmitter connection:

- An Endress+Hauser iTEMP TMT82 temperature transmitter with two channels and HART® protocol is used. One channel converts the signals of the temperature sensor to a 4 to 20 mA signal. The second channel uses the sensor breakage detection function in the thermocouple configuration and transmits this failure information via the HART® protocol if the pressure switch is activated. Other configurations are possible on request.
- An Endress+Hauser iTEMP TMT86 temperature transmitter with two channels and PROFINET® protocol are used. A channel converts the temperature sensor signals for the PROFINET® communication. The second channel uses the sensor breakage detection function and transmits this failure information via the PROFINET® protocol if the pressure switch is activated.



A0038482

27 Extension neck with second process seal

- 1 Terminal head with built-in temperature transmitter
- 2 Housing with dual cable entry. A suitable cable gland is installed for the cable entry of the pressure switch. The second cable entry is not assigned.
- 3 Second process seal
- 4 Installed pressure switch
- 5 Upper part of the thermowell

Maximum pressure	200 bar (2 900 psi)
Switch point	3.5 bar (50.8 psi) ± 1 bar (± 14.5 psi)
Ambient temperature range	-20 to +80 °C (-4 to +176 °F)
Process temperature range	Up to +400 °C (+752 °F), minimum required length of extension neck T = 100 mm (3.94 in)
Seal material	FKM

i During the design phase, pay attention to the significantly lower pressure resistance of the thermowell and process connection as well as the resistance of the seal material to the process medium!


The primary thermowell, whose material can be selected from various stainless steels or nickel-based materials, represents the first process seal. The resistance of the thermowell material to the process conditions must be guaranteed. The extension neck represents the second process seal. The process here is sealed off from the environment by means of seals made of FKM. The resistance of the seal material to the process conditions must be guaranteed.

i Recommendation: Due to the aging of the internal seals, we recommend replacing the components of the second process seal every five years, even if no fault has occurred in the thermowell. In the event of a leak in the thermowell, the components of the second process seal must be replaced along with the thermowell. If, as a result of the leak in the first process seal, the pressure in the extension neck rises above the switching pressure of the pressure switch, the transmitter transmits a "sensor break" error message to the control system via HART® communication.

Pre-defined versions

i Pre-defined standard geometries apply if no other options for special geometries are selected in the optional configuration section.

Thermometer with thermowell according to ASME standard



A0052234


The pre-defined geometries are the result of combining the thermowell standard, the process connection and the geometry of the wetted parts.

Thermowell standard	Process connection	Geometry of wetted parts	Root \varnothing D1	Tip \varnothing D2	Bore \varnothing Di	Bottom thickness B	Flange face	Thermometer connection Ge1	Lagging- \varnothing De1
Metric ASME with flange	Flange 1"/DN25	Straight	19 mm (0.75 in)	19 mm (0.75 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	RF	NPT 1/2"	32 mm (1.26 in)
		Tapered	22.2 mm (0.87 in)	15 mm (0.6 in)					
		Stepped	19 mm (0.75 in)	12.7 mm (0.5 in)					
	Flange 1 1/2"/DN40	Straight	19 mm (0.75 in)	19 mm (0.75 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	RF	NPT 1/2"	32 mm (1.26 in)
		Tapered	27 mm (1.06 in)	17 mm (0.67 in)					
		Stepped	19 mm (0.75 in)	12.7 mm (0.5 in)					
	Flange 2"/DN50	Straight	19 mm (0.75 in)	19 mm (0.75 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	RF	NPT 1/2"	32 mm (1.26 in)
		Tapered	27 mm (1.06 in)	17 mm (0.67 in)					
		Stepped	19 mm (0.75 in)	12.7 mm (0.5 in)					
Metric ASME with thread	NPT 1/2", G 1/2", M20 male thread	Straight	16 mm (0.63 in)	16 mm (0.63 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	30 mm (1.18 in) ¹⁾
		Tapered		15 mm (0.6 in)					
		Stepped		12.7 mm (0.5 in)					
	NPT 3/4" male thread	Straight	19 mm (0.75 in)	19 mm (0.75 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	30 mm (1.18 in) ¹⁾
		Tapered	19.5 mm (0.77 in)	15 mm (0.6 in)					
		Stepped	19 mm (0.75 in)	12.7 mm (0.5 in)					
	NPT 1", male thread	Straight	22.2 mm (0.87 in)	22.2 mm (0.87 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	35 mm (1.38 in)
		Tapered	27 mm (1.06 in)	17 mm (0.67 in)					
		Stepped	22.2 mm (0.87 in)	12.7 mm (0.5 in)					
	M27x2	Straight	19 mm (0.75 in)	19 mm (0.75 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	35 mm (1.38 in)

Thermowell standard	Process connection	Geometry of wetted parts	Root \varnothing D1	Tip \varnothing D2	Bore \varnothing Di	Bottom thickness B	Flange face	Thermometer connection Ge1	Lagging- \varnothing De1
		Tapered	19.5 mm (0.77 in)	15 mm (0.6 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	40 mm (1.57 in) ²⁾
		Stepped	19 mm (0.75 in)	12.7 mm (0.5 in)					
	M33x2	Straight	22.2 mm (0.87 in)	22.2 mm (0.87 in)					
		Tapered	27 mm (1.06 in)	17 mm (0.67 in)					
		Stepped	22.2 mm (0.87 in)	12.7 mm (0.5 in)					
Metric ASME for weld-in	NPS 3/4", 26.7 mm	Tapered	26.7 mm (1.05 in)	17 mm (0.67 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	26.7 mm
	NPS 1", 33.4 mm	Tapered	33.4 mm (1.31 in)	20 mm (0.79 in)					33.4 mm
Metric ASME with socket weld	NPS 3/4", 26.7 mm	Straight	19 mm (0.75 in)	19 mm (0.75 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	26.7 mm
		Tapered	22.2 mm (0.87 in)	15 mm (0.6 in)					
		Stepped	19 mm (0.75 in)	12.7 mm (0.5 in)					
	NPS 1", 33.4 mm	Straight	25.4 mm (1.0 in)	25.4 mm (1.0 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	-	NPT 1/2"	33.4 mm
		Tapered	25.4 mm (1.0 in)	15 mm (0.6 in)					
		Stepped	22.2 mm (0.87 in)	12.7 mm (0.5 in)					

- 1) 27 mm (1.06 in) for material: carbon steel and CrMo steel/Mo steel
- 2) 50 mm (1.97 in) for material: carbon steel and alloy

Thermometer with thermowell according to DIN standard



A0052237


The pre-defined geometries are the result of combining the thermowell standard and the selected extension neck including the thermometer connection

Thermowell standard	Extension neck	Geometry of wetted parts	Root \varnothing D1	Tip \varnothing D2	Bore \varnothing Di	Bottom thickness B	Flange face	Thermometer connection Ge1	Lagging- \varnothing De1	
DIN 43772 Form 4F, flanged	Standard	Tapered	18 mm (0.71 in)	9 mm (0.35 in)	3.5 mm (0.14 in) ¹⁾	6 mm (0.24 in)	B1	M14x1.5	18 mm (0.71 in)	
			24 mm (0.95 in)	12.5 mm (0.5 in)	6.5 mm (0.26 in)			M18x1.5	24 mm (0.95 in)	
			26 mm (1.02 in)	12.5 mm (0.5 in)	6.5 mm (0.26 in)			G ½"	26 mm (1.02 in)	
	24 mm (0.95 in)		12.5 mm (0.5 in)	6.5 mm (0.26 in)	M18x1.5			24 mm (0.95 in)		
QuickNeck or with second process seal	Standard		18 mm (0.71 in)	9 mm (0.35 in)	3.5 mm (0.14 in) ¹⁾			-	M14x1.5	18 mm (0.71 in)
Standard			24 mm (0.95 in)	12.5 mm (0.5 in)	6.5 mm (0.26 in)				M18x1.5	24 mm (0.95 in)
			26 mm (1.02 in)	12.5 mm (0.5 in)	6.5 mm (0.26 in)				G ½"	26 mm (1.02 in)
			QuickNeck or with second process seal	24 mm (0.95 in)	12.5 mm (0.5 in)				6.5 mm (0.26 in)	M18x1.5

1) For L > 110 mm (4.33 in), a stepped bore is used: (6.5 mm (0.26 in) > 3.5 mm (0.14 in))

Length combination according to DIN 43772	
Form 4, weld-in	Form 4 F, flanged, standard extension neck
L = 110 mm (4.3 in), C1 = 65 mm (2.56 in)	L = 200 mm (7.87 in), U = 130 mm (5.12 in), C1 = 65 mm (2.56 in)
L = 110 mm (4.3 in), C1 = 73 mm (2.87 in)	L = 260 mm (10.24 in), U = 190 mm (7.5 in), C1 = 125 mm (4.92 in)
L = 140 mm (5.51 in), C1 = 65 mm (2.56 in)	L = 410 mm (16.14 in), U = 340 mm (13.39 in), C1 = 275 mm (10.83 in)
L = 170 mm (6.7 in), C1 = 133 mm (5.24 in)	
L = 200 mm (7.87 in), C1 = 125 mm (4.92 in)	

Thermometer with thermowell according to NAMUR standard




A0052239

The pre-defined geometries result from the thermowell standard

Thermowell standard	Process connection size	Geometry of wetted parts	Root \varnothing D1	Tip \varnothing D2	Bore- \varnothing Di (Di1 > Di2)	Bottom thickness B	Flange face	Thermometer connection Ge1
Metric, based on NAMUR NE170, flanged	Flange DN25-DN80	Tapered	20 mm (0.79 in)	13 mm (0.51 in)	Stepped, 7 mm (0.28 in) > 6.1 mm (0.24 in)	7 mm (0.28 in)	B1	Male thread M24x1.5, adjustable

Thermometer with iTHERM TwistWell thermowell



A0052240

The pre-defined geometry results from the iTHERM TwistWell (version: 30 mm (1.18 in)).

Thermowell type	Process connection size	Geometry of wetted parts	Root \varnothing D1	Tip \varnothing D2	Bore \varnothing Di	Bottom thickness B	Flange face	Thermometer connection Ge1	Lagging- \varnothing De1
iTHERM TwistWell, flanged	Every selectable flange size	Unstreamed length	30 mm (1.18 in)	22 mm (0.87 in)	6.5 mm (0.26 in)	6 mm (0.24 in)	B1/RF	NPT 1/2" ¹⁾	30 mm (1.18 in)

1) According to feature 030, or NPT1/2" if not defined

Certificates and approvals

Current certificates and approvals for the product are available at www.endress.com on the relevant product page:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Downloads**.

Test on thermowell

Thermowell pressure tests are carried out in accordance with the specifications in DIN 43772. With regard to thermowells with tapered or reduced tips that do not comply with this standard, these are tested using the pressure of corresponding straight thermowells. Sensors for use in hazardous areas are also always subjected to a comparative pressure during the tests. Tests according to other specifications can be carried out on request. The liquid penetration test verifies that there are no cracks in the welded seams of the thermowell.

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Configuration**.



Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Accessories

The accessories currently available for the product can be selected at www.endress.com:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Spare parts & Accessories**.

Service-specific accessories

Applicator

Software for selecting and sizing Endress+Hauser measuring devices:

- Calculation of all the necessary data for identifying the optimum measuring device: e.g. pressure loss, accuracy or process connections.
- Graphic illustration of the calculation results

Administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.

Applicator is available:

<https://portal.endress.com/webapp/applicator>

Configurator

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

The Configurator is available on the Endress+Hauser website: www.endress.com -> Click "Corporate" -> Select your country -> Click "Products" -> Select the product using the filters and the search field -> Open the product page -> The "Configure" button to the right of the product image opens the Product Configurator.

DeviceCare SFE100

Configuration tool for HART, PROFIBUS and FOUNDATION Fieldbus field devices

DeviceCare is available for download at www.software-products.endress.com. You need to register in the Endress+Hauser software portal to download the application.



Technical Information TI01134S

FieldCare SFE500

FDT-based plant asset management tool

It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.



Technical Information TI00028S

Netilion

IloT ecosystem: Unlock knowledge


With the Netilion IloT ecosystem, Endress+Hauser enables you to optimize plant performance, digitize workflows, share knowledge, and enhance collaboration. Drawing on decades of experience in process automation, Endress+Hauser provides the process industry with an IloT ecosystem that unlocks valuable insights from data. These insights allow process optimization, leading to increased plant availability, efficiency, and reliability - ultimately resulting in a more profitable plant.



www.netilion.endress.com

Supplementary documentation

The following types of documentation are available on the product pages and in the Download Area of the Endress+Hauser website (www.endress.com/downloads) (depending on the selected device version):

Document	Purpose and content of the document
Technical Information (TI)	Planning aid for your device The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.
Brief Operating Instructions (KA)	Guide that takes you quickly to the 1st measured value The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning.
Operating Instructions (BA)	Your reference document The Operating Instructions contain all the information that is required in various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal.
Description of Device Parameters (GP)	Reference for your parameters The document provides a detailed explanation of each individual parameter. The description is aimed at those who work with the device over the entire life cycle and perform specific configurations.
Safety Instructions (XA)	Depending on the approval, Safety Instructions (XA) are supplied with the device. The Safety Instructions are an integral part of the Operating Instructions.  Information on the Safety Instructions (XA) that are relevant for the device is provided on the nameplate.
Supplementary device-dependent documentation (SD/FY)	Always comply strictly with the instructions in the relevant supplementary documentation. The supplementary documentation is an integral part of the device documentation.



www.addresses.endress.com
