# GM32

In-situ gas analyzer for efficient measurement of  $SO_2$ , NO, NO<sub>2</sub>, NH<sub>3</sub> – even in ATEX zones

#### Measure aggressive gases directly and quickly – even in ATEX zones

- Nearly uncompromised measured values measured directly in the gas duct
- Short-term process deviations can be measured
- Representative measurement by selection of cross-duct or measuring probe type
- Fast on-site service possible due to modular design
- Long maintenance-free intervals
- Cost-effective in-situ gas analyzer – Ex-type also available
- Low cost of installation and operation, no test gases required





# Cleaner environment thanks to our proven measurement technology

Since the beginning of industrialization, air pollution caused by exhaust gases and environmental impact has been a challange that needs to be addressed. In order to comply with limit values and protect the environment from further pollution, it is necessary to measure accurately and monitor reliably at the crucial points. For decades, we have been working with our customers on innovative solutions that have proven themselves thousands of times to make an effective contribution to environmental protection. In-situ measurement technology offers many advantages for continuous gas analysis. It delivers accurate results directly, quickly and without expensive gas extraction and transportation. In addition to compliance with limit values, the GM32 gas analyzer also significantly increases plant efficiency and ensures optimum process control while minimizing maintenance costs. The gas analyzers in the GM32 product family measure  $SO_2$ , NO,  $NO_2$  and  $NH_3$  simultaneously and continuously 24/7, 365 day a year.




# Versatile success – the all-rounder for many industries and applications

Every industry also produces exhaust gases. The GM32 therefore offers efficient solutions for a wide range of requirements. Different device variants enable process access for every application. With its robust in-situ measurement technology, the GM32 proves its worth in both emission monitoring and process control - day in, day out in all its fields of application.

#### GM32 overview GM32 standard versions **GM32 Ex versions** Version Measurement components SO<sub>2</sub> V V NO V V $NO_2$ V V V V NH₃ Temperature V V Pressure V V Process access (plant) Cross duct version V V V Open measuring probe version V V Measuring probe with gas permeable filter element Maximum temperature Up to + 550 °C (+ 1,020 °F) V V Ex zones \_ Zone 2 ATEX / IEC Ex \_ Non-ex area V V

# Advantages through intelligent design

Environmental protection and process optimization are not that complicated and costly. The GM32 proves this with its robustness, uncomplicated installation and automatic selftesting. They ensure long maintenance-free intervals and minimal maintenance costs. The compact connection unit with many outputs and connection options allows remote data retrieval and remote maintenance anywhere in the world. The fast response time due to the in-situ technology and the high accuracy of the measurement results optimize process control and the balance between economic efficiency and environmental compatibility.





#### AAC (Automatic Alignment Correction)

#### Advantage:

Thanks to automatic beam tracking of the optical path, the GM32 measures reliably even in the event of strong vibrations.

#### Cross duct or measuring probe version

#### Advantage:

High flexibility in adapting to the respective application, representative measurement results through selection of cross-duct or measuring probe version.



# Flexible process access

#### Version with open measuring probe (GMP)

**Device components** 

- Sender/receiver unit
- GMP measuring probe with open design

#### Advantages

- Very fast response time
- Mounting from only one side
- High gas or dust concentrations possible
- With various measuring paths
- With integrated zero-point path

#### **Cross-duct version**

- **Device components**
- Sender/receiver unit
- Reflector unit

#### Advantages

- Very fast response time
- Non-contact measurement with aggressive or hot gases
- Representative results even with duct diameters of up to 12 m (40 ft)
- Insenstive to swiveling due to automatic self-alignment of the measuring path



## Version with gas-testable measuring probe (GPP)

#### **Device components**

- Sender/receiver unit
- GPP measuring probe with permeable filter element for adjustment with test gases

#### Advantages

- Mounting only from one side
- High gas or dust concentrations possible
- With various measuring paths
- With integrated zero-point paths
- Stable results even with turbulent gas flows
- Gas testing according to U.S. EPA possible



# For industrywide measurment tasks

#### Denitrification (DeNO<sub>x</sub>)

The key factor for efficient monitoring and control of the flue gas denitrification plant is a very short response time of the measurement. This can significantly increase the efficiency and service life of the plant and at the same time avoid follow-up costs due to pollutant loads caused by ammonia in the fly ash. The GM32 provides reliable measurement results in real time for monitoring NO concentrations in both the raw gas and clean gas ducts as well as for NH<sub>3</sub> slip measurement downstream of the catalytic converter. Only one analyzer for NO, NO<sub>2</sub> and NH<sub>3</sub> means less installation and maintenance effort.

#### **Desulphurization (DeSO<sub>x</sub>)**

Here too, the GM32 proves its worth in process control and continuous emission measurement. Regardless of whether the sample gases are saturated (wet) or dry. The fast GM32 analyzer with its direct, delay-free in-situ measurement of  $SO_2$  is the ideal analyzer for the efficient monitoring and control of flue gas cleaning systems.

#### **Emission measurements**

For years, our in-situ analyzers have been characterized by minimal operating costs. Thanks to this technology, maintenance costs and problems caused by gas transportation and gas treatment do not arise in the first place. The measured value is virtually recorded in the active measuring section directly in the gas duct. Adjustment with test gases is not necessary. In addition, the QAL3 control without test gases is the last logical step in achieving very low operating costs. Thanks to the automatic self-test function, you can rely on the measured values and are warned in good time in the event of deviations.

#### **Process control in CPR plants**

The GM32 Ex is also available for non-contact measurement thanks to the cross-duct version and is of interest to the chemical, natural gas and petroleum industries. The pressurized version can be used in Ex zones 1 and 2 with ATEX class 3G or 2G up to 650  $^{\circ}$ C (1,200  $^{\circ}$ F). GM32 Ex can be applied as an emission measuring instrument downstream of sulphur recovery units or FCC crackers.



# GM32: Measure aggressive gases directly and quickly – even in ATEX zones



#### **Product Description**

The GM32 in-situ gas analyzer measures  $SO_2$ , NO,  $NO_2$  and  $NH_3$ , pressure and temperature in the gas duct. Direct, fast and without gas sampling and transport. This means that control systems work directly with almost uncompromised values. Due to self-monitoring, the measured values

#### At a glance

- Direct, fast in-situ measurement
- No gas sampling, no gas transport, no gas conditioning
- Up to four measurands at the same time, plus process temperature and pressure
- DOAS evaluation methods

#### Your benefits

- Nearly uncompromised measured values measured directly in the gas duct
- Short-term process deviations can be measured
- Representative measurement by selection of cross-duct or measuring probe type

#### **Fields of application**

- For monitoring and control in flue gas purification, such as denitrification plants, desulfurization plants and converters
- Emissions monitoring according to EU directives or local regulations

are reliable. In case of a malfunction, an early warning will be shown. For emission measurement of  $SO_2$  and NO, the GM32 is tested for suitability according to European standard EN 15267. An Ex-type with extensive safety functions and sophisticated system technology is also available.

- Numerous independent measuring ranges with consistent accuracy
- Automated self-test function (QAL3) without test gases
- Overpressure encapsulated type for Ex-zone 2
- Fast on-site service possible due to modular design
- Long maintenance-free intervals
- Cost-effective in-situ gas analyzer Ex-type also available
- Low cost of installation and operation, no test gases required
- Monitoring of landfill gases
- Monitoring tasks, for example, in nitric acid and ammonia production processes



#### More Information online

For more information, enter the link or scan the QR code to get direct access to technical data, operating instructions, software, application examples, and much more. www.endress.com/gm32



# **Technical Data**

The precise device specifications and product performance data may vary and are dependent on the respective application and customer specifications.

iM32 general	
Measured values	NO, NO <sub>2</sub> , NH <sub>3</sub> , SO <sub>2</sub>
Performance-tested measurands	NO, SO <sub>2</sub>
Maximum number of measurands	4 (plus process temperature and pressure)
Measurement principles	Differential optical absorption spectroscopy (DOAS)
Measuring ranges	
NH <sub>3</sub>	0 30 ppm / 0 2,600 ppm
NO	0 40 ppm / 0 1,900 ppm
NO <sub>2</sub>	0 50 ppm / 0 1,000 ppm
SO <sub>2</sub>	0 32 ppm / 0 7,000 ppm
LowNO <sub>2</sub>	0 20 ppm / 0 1,000 ppm
	Measuring ranges refer to 1 m measuring path Measuring ranges depend on application and device version
Certified measuring ranges	
NO	0 70 mg/m <sup>3</sup> ; 0 700 mg/m <sup>3</sup> ; 0 1,300 mg/m <sup>3</sup>
SO <sub>2</sub>	0 75 mg/m <sup>3</sup> ; 0 1,000 mg/m <sup>3</sup> ; 0 2,500 mg/m <sup>3</sup>
Remark	With an active measuring path length of 1.86 m (cross duct) or 1.25 m (open path measuring probe) The gas-testable measuring probe (GPP) is not TUV approved
Response time (t <sub>90</sub> )	
Open measuring probe (GMP):	≥ 5 s
Gas-testable measur. probe (GPP):	≥ 120 s
Cross-duct version:	≥ 5 s
Remark	Response time adjustable
Accuracy	
NH <sub>3</sub> :	± 2 %
NO:	± 2 %
NO <sub>2</sub> :	± 2 %
SO <sub>2</sub> :	± 2 %
Remark	Relative to the smallest measuring range
Ambient temperature	-20 °C +55 °C (−4 °F + 131 °F); temperature change max. ±10 °C/h
Storage temperature	$-20 \degree$ +55 $\degree$ (-4 $\degree$ + 131 $\degree$ ); temperature change max. ±10 $\degree$ C/h
Ambient humidity	Solution of the second seco

Conformities	Approved for plants requiring approval 2001/80/EC (13. BlmSchV) 2000/76/EC (17. BlmSchV) 27 <sup>th</sup> BlmSchV TA-Luft (Prevention of Air Pollution) EN 15267 EN 14181 MCERTS GOST
Ex-approvals	
IECEx	Ex pzc op is [ia] IIC T3 Gc
ATEX	II 3G Ex pzc op is [ia] IIC T3 Gc
Electrical safety	CE
Mounting	Mounting flange, DN125, PN6 Mounting flange, ANSI, 5"
Test functions	Internal zero point check Check cycle for zero and span point according to QAL3
Options	SCU control unit (for non-hazardous areas only) Multi range calibration (additional measuring ranges for one component) Extended gas temp. range up to 550 °C or 650 °C (1,020 °F or 1,200 °F) LowNO <sub>2</sub>

### Open measuring probe (GMP)

Description	Measuring probe in open design with integrated purge air control system
Measuring distance	See dimensional drawings
Accuracy	
Pressure sensor:	1 %
Temperature sensor:	1 %
Process temperature	≤ + 550 °C (≤ + 1,020 °F)
Process pressure	-60 hPa 30 hPa (-0.9 psi 0.4 psi), depending on purge air supply
Dust load	$\leq$ 3 g/m <sup>3</sup> , based on a 1 m measuring distance, depending on application
Electrical safety	CE
Dimensions (W x H x D)	Dimensions may vary. For details, see the dimensional drawings.
Weight	See dimensional drawings
Material in contact with media	Stainless steel 1.4571, stainless steel 1.4539
Power supply	
Voltage	Supply via sender/receiver unit
Auxiliary gas connections	
Purge air	Hose nozzle 40 mm (1.6")
Integrated components	Flow monitor for purge air monitoring PT1000 temperature sensor Pressure sensor

#### Gas-testable measuring probe (GPP)

Description	Measuring probe with gas permeable filter element for adjustment with test gas
Measuring distance	See dimensional drawings
Accuracy	
Pressure sensor:	1 %
Temperature sensor:	1 %
Process temperature	
With ceramic filter	$\leq$ +430 °C ( $\leq$ +805 °F); brief (max. 30 min.) up to 550 °C (1,020 °F). At temperatures higher than 430 °C (805 °F), reliable output of measured values can no longer be guaranteed.
NH₃ measurement w. ceramic filter	$NH_3$ measurement with ceramic filter +300 +430 °C (+572 805 °F); brief (max. 30 min.) up to 550 °C (1,020 °F). At temperatures higher than 430 °C (805 °F), reliable output of measured values can no longer be guaranteed.
With Teflon filter	≤ +200 °C (≤ +392 °F)
Process pressure	-120 hPa 200 hPa (-1.7 psi 2.9 psi)
Dust load	$\leq 30 \text{ g/m}^3$
Electrical safety	CE
Enclosure rating	IP 65
Dimensions (W x H x D)	Dimensions may vary. For details, see the dimensional drawings.
Weight	See dimensional drawings
Material in contact with media	Stainless steel 1.4571, stainless steel 1.4539, ceramics, PTFE
Power supply	
Voltage:	115 V AC, ± 10 % 230 V AC, ± 10 %
Frequency	50 Hz / 60 H
Power consumption	≤ 150 VA
Auxiliary gas connections	
Test gas	Clamp connection 1/4"
Integrated components	Pressure sensor PT1000 temperature sensor Heating of optical surfaces

#### Sender/receiver unit: standard version

Description	Analyzer unit of the measuring device
Electrical safety	CE
Enclosure rating	IP 65 / IP 69K
Operation	Via integrated control unit
Dimensions (W x H x D)	239 mm x 316 mm x 338 mm (for details see dimensional drawings) (9.4" x 12.4" x 13.3") (for details see dimensional drawings)
Weight	20 kg (44 lbs)
Power supply	
Voltage:	24 V DC, supply via sender/receiver unit
Power consumption	≤ 36 W

#### Sender/receiver unit: Ex-version

Description	Analyzer unit of the measuring device
Electrical safety	CE
Enclosure rating	IP 65 / IP 69K
Operation	Via integrated control unit
Dimensions (W x H x D)	315 mm x 910 mm x 410 mm (for details see dimensional drawings) (12.4" x 35.8" x 16.1") (for details see dimensional drawings)
Weight	20 kg (44 lbs)
Power supply	
Voltage:	24 V DC, supply via sender/receiver unit
Power consumption	≤ 36 W

#### Connection unit: standard version

Description	Serves for connection of power supply, data and signal cabling provided by the customer
Electrical safety	CE
Enclosure rating	IP 65 / IP 69K
Analog outputs	2 outputs: 0/4 22 mA, 500 $\Omega$ Per module, extendable up to eight outputs
Analog inputs	2 inputs: 0/4 22 mA, 100 Ω
Digital outputs	4 outputs: 48 V AC/DC, 0.5 A, 25 W
Digital inputs	4 inputs: 3.9 V, 4.5 mA, 0.55 W Per module, extendable up to eight inputs
Modbus	V
Type of fieldbus integration	TCP RTU RS-485 (via optional interface module)

CAN bus	$\checkmark$
Function	Internal system bus
Ethernet	V
Function	Connection to SOPAS ET software or OPC server
Dimensions (W x H x D)	450 mm x 424 mm x 158 mm (for details see dimensional drawings) (17.7" x 16.7" x 6.2") (for details see dimensional drawings)
Weight	16 kg (7.3 lbs)
Power supply	
Voltage	100 V AC 250 V AC, ± 10 %
Frequency	50 Hz / 60 Hz
Power consumption	≤ 260 VA

#### Connection unit: Ex-version

Description	Serves for connection of power supply, data and signal cabling provided
	by the customer
Electrical safety	CE
Enclosure rating	IP 65 / IP 69K
Analog outputs	2 outputs: 0/4 22 mA, 500 $\Omega$ Per module, extendable up to eight outputs
Analog inputs	2 inputs: 0/4 22 mA, 100 Ω
Digital outputs	4 outputs: 48 V AC/DC, 0.5 A, 25 W
Digital inputs	4 inputs: 3.9 V, 4.5 mA, 0.55 W Per module, extendable up to eight inputs
Modbus	$\checkmark$
Type of fieldbus integration	TCP RTU RS-485 (via optional interface module)
CAN bus	V
Function	Internal system bus
Ethernet	V
Function	Connection to SOPAS ET software or OPC server
Dimensions (W x H x D)	679 mm x 630 mm x 158 mm (for details see dimensional drawings) (26.7" x 24.8" x 6.2") (for details see dimensional drawings)
Weight	16 kg (7.3 lbs)
Power supply	
Voltage	100 V AC 250 V AC, ± 10 %
Frequency	50 Hz / 60 Hz
Power consumption	≤ 260 VA

Description	Flange fixture for connections for purge air hose, temperature and pres- sure sensor
Electrical safety	CE
Dimensions (W x H x D)	309 mm x 364 mm x 242 mm (for details see dimensional drawings) (12.2" x 14.3" x 9.5") (for details see dimensional drawings)
Weight	9.6 kg (21.2 lbs)
Auxiliary gas connections	
Purge air	Hose nozzle 40 mm (1.6")
Electrical connections	Purge air unit low-pressure monitor PT1000 temperature sensor Pressure sensor
Integrated components	Flow monitor for purge air monitoring Pressure sensor

### Purge air fixture: reflector unit

Purge air fixture: sender/receiver unit

Description	Flange fixture for connections for purge air hose and purge air monitoring
Electrical safety	CE
Dimensions (W x H x D)	309 mm x 364 mm x 242 mm (for details see dimensional drawings) (12.2" x 14.3" x 9.5") (for details see dimensional drawings)
Weight	9.6 kg (21.2 lbs)
Auxiliary gas connections	
Purge air	Hose nozzle 40 mm (1.6")
Electrical connections	Purge air unit low-pressure monitor
Integrated components	Flow monitor for purge air monitoring

#### Pressure and termperature sensor (cross-duct version)

Description	Pressure and temperature sensor with DN40 / PN40 mounting flange
Accuracy	
Pressure sensor	1 %
Temperature sensor	1 %
Process temperature	≤ +500 °C (≤ +1,020 °F)
Electrical safety	CE
Dimensions (W x H x D)	Dimensions may vary. For details, see the dimensional drawings.
Immersion depth	
PT1000 temperature sensor	500 mm (19.7") 1,000 mm (39.4") 1,400 mm (55.1")
Material	Stainless steel 1.4571, steel ST37
Scope of delivery	Connecting cable for temperature sensor, 5 m (16.4 ft) Connecting hose for pressure sensor, 5 m (16.4 ft) Flange cover, including seal and screws

#### SLV4-2 purge air unit, 2BH1300, 3-ph


Description	Unit to provide dust-free air for flushing of optical surfaces				
Gas flow rate	38 m <sup>3</sup> /h 63 m <sup>3</sup> /h (1.3 ft <sup>3</sup> /hr 2.2 ft <sup>3</sup> /hr) At 30 hPa (0.4 psi) counter pressure, dep. on low pressure inside the f				
Ambient temperature	-40 °C +55 °C (-40 °F +131 °F)				
Electrical safety	CE				
Enclosure rating	IP 54				
Dimensions (W x H x D)	550 mm x 550 mm x 258 mm (for details see dimensional drawings) (21.7" x 21.7" x 10.2") (for details see dimensional drawings)				
Weight	18 kg (40 lbs)				
Power supply					
Three-phase current	Δ: 200 240 V AC, 50 Hz, 2,6 A, 400 VA Y: 345 415 V AC, 50 Hz, 1,5 A, 400 VA Δ: 200 275 V AC, 60 Hz, 2,6 A, 500 VA Y: 380 480 V AC, 60 Hz, 1,5 A, 500 VA Δ: 270 330 V AC, 50 Hz, 2,0 A, 400 VA Y: 465 570 V AC, 50 Hz, 1,16 A, 400 VA Δ: 290 360 V AC, 60 Hz, 2,1 A, 500 VA Y: 500 600 V AC, 60 Hz, 1,26 A, 500 VA Δ: 230 V AC, 50 Hz, 2,7 A, 370 VA Δ: 115 V AC, 60 Hz, 3,0 A, 450 VA Δ: 220 270 V AC, 50 Hz, 2,5 A, 400 VA Y: 380 465 V AC, 50 Hz, 1,45 A, 400 VA Δ: 240 290 V AC, 60 Hz, 1,55 A, 500 VA				
Auxiliary gas connections					
Purge air	40 mm (1.6")				
Test functions	Pressure switch (switching point –35 hPa (–0.5 psi))				
Integrated components	2-step air filter, type Europiclon, dust capacity 200 g				


# **Order Information**

Our regional sales organization will be glad to advise you on which device configuration is best for you.


## **Dimensional drawings**

Sender/receiver unit; standard version (dimensions in mm (inch))





## Sender/receiver unit; Ex-version (dimensions in mm (inch))




## Open measuring probe (GMP) (dimensions in mm (inch)

#### GMP measuring probes

		Measuring gap L3 (active measuring path)							
		250	500	750	1,000	1,250	1,500	1,750	
		(9.8)	(19.7)	(29.5)	(39.4)	(49.2)	(59.1)	(68.9)	
Probe length <sup>*</sup>	L1				L2				
900 (35.4)	935 (36.8)	296 (11.7)							21 (46.3)
1,500 (59.1)	1,644 (64.7)	1,005 (39.6)	755 (29.7)	505 (19.9)	255 (10.0)				24 (52.9)
2,000 (78.7)	2,128 (83.8)	1,489 (58.6)	1,239 (48.8)	989 (38.9)	739 (29.1)	489 (19.3)	239 (9.4)		30 (66.1)
2,500 (98.4)	2,628 (103.5)	1988 (78.3)	1,738 (68.4)	1,488 (58.6)	1,238 (48.7)	988 (38.9)	738 (29.1)	488 (19.2)	35 (77.2)
* Probe lenat	h. nominal								

All dimensions in mm (inch), weight in kg (lbs)

Application specific lengths on request



## Gas-testable measuring probe (GPP) (dimensions in mm (inch)


#### Gas-testable measuring probe (GPP)


		Mea	Weight			
		227 (8.9)	477 (18.8)	727 28.6)	977 (38.5)	
Probe length <sup>*</sup>	L1					
900 (35.4)	914 (35.9)	353 (13.9)	103 (4.1)			27 (59.5)
1,500 (59.1)	1,624 (63.9)	1,063 (41.9)	813 (32.0)	563 (22.2)	313 (12.3)	35 (77.2)
2,000 (78.7)	2,108 (83.0)	1,547 (60.9)	1,297 (51.1)	1,047 (41.2)	797 (31.4)	42 (92.6)
2,500 (98.4)	2,608 (102.7)	2,047 (80.6)	1,797 (70.7)	1,547 (60.9)	1,297 (51.1)	50 (110)
*						


\* Probe length, nominal


All dimensions in mm (inch), weight in kg (lbs) Application specific lengths on request

## GM32 reflector unit (dimensions in mm (inch))

















## Connection unit; Ex-version (dimensions in mm (inch))





## SLV4-2 purge air unit, 2BH1300 (dimensions in mm (inch))



www.addresses.endress.com

