Technical Information **Proline Promag W 300**

Electromagnetic flowmeter



Specialist for demanding water and wastewater applications with a compact, easily accessible transmitter

Application

- The bidirectional measuring principle is virtually independent of pressure, density, temperature and viscosity
- Suitable for elementary measurement tasks such as raw water intake

Device properties

- International drinking water approvals
- Degree of protection IP68 (Type 6P enclosure)
- Compact dual-compartment housing with up to 3 I/Os
- Backlit display with touch control and WLAN access
- Remote display available

Your benefits

- Reliable measurement at constant accuracy with 0 x DN inlet run and no pressure loss
- Flexible engineering sensor with fixed or lap-joint process connections
- Long-term operation robust and completely welded sensor
- Improved plant availability sensor compliant with industry-specific requirements
- Full access to process and diagnostic information numerous, freely combinable I/Os and Ethernet
- Reduced complexity and variety freely configurable I/O functionality
- Integrated verification Heartbeat Technology



Table of contents

About this document		Relative humidity	
Symbols	. 4	Operating height	
		Degree of protection	
Function and system design	5	Vibration- and shock-resistance	
Measuring principle		Mechanical load	
Measuring system		Electromagnetic compatibility (EMC)	66
Equipment architecture		Process	66
Security	. /	Medium temperature range	
Input	. 9	Conductivity	
Measured variable	. 9	Pressure/temperature ratings	
Measuring range	. 9	Pressure tightness	
Operable flow range		Flow limit	
Input signal		Pressure loss	
1 3		System pressure	
Outunt	1 -	Thermal insulation	
Output	15	Vibrations	
Output and input variants		Magnetism and static electricity	. /2
Output signal			
Signal on alarm		Custody transfer mode	73
Load			
Ex connection data	25	Mechanical construction	73
Low flow cut off	26	Dimensions in SI units	
Galvanic isolation	27		
Protocol-specific data	27	Dimensions in US units	
		Weight	
Power supply	34	Measuring tube specification	
Terminal assignment	34	Materials	102
Available device plugs	35	Fitted electrodes	105
Supply voltage	36	Process connections	105
Power consumption	36	Surface roughness	105
Current consumption	36		
Power supply failure	36	Operability	106
Overcurrent protection element		Operating concept	106
Electrical connection	37	Languages	106
Potential equalization	47	Local operation	106
Terminals	50	Remote operation	107
Cable entries	50	Service interface	113
Pin assignment, device plug	51	Network integration	114
Cable specification		Supported operating tools	
Overvoltage protection		HistoROM data management	
o certaining proceedings of the certain of the cert		g	
Performance characteristics	55	Certificates and approvals	118
Reference operating conditions	55	CE mark	118
Maximum measured error	55	UKCA marking	118
Repeatability	58	RCM mark	118
Influence of ambient temperature	58	Ex approval	118
•		Drinking water approval	119
Installation	EO	HART certification	119
Installation		FOUNDATION Fieldbus certification	119
Mounting location		Certification PROFIBUS	119
Orientation	61	EtherNet/IP certification	119
Inlet and outlet runs	62	Certification PROFINET	120
Adapters	64	Certification PROFINET with Ethernet-APL	120
Special mounting instructions	65	Radio approval	120
		Other standards and guidelines	120
Environment			
Ambient temperature range	65	Ordering information	120
Storage temperature	65		

2

Application packages	121
Diagnostic functionality	121
Heartbeat Technology	121
Cleaning	121
OPC-UA Server	122
Accessories	122
Device-specific accessories	
Communication-specific accessories	
Service-specific accessories	
System components	124
Supplementary documentation	125
Standard documentation	
Supplementary device-dependent documentation	
Registered trademarks	127

About this document

Symbols Electrical symbols

Symbol	Meaning
===	Direct current
~	Alternating current
$\overline{}$	Direct current and alternating current
=	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Potential equalization connection (PE: protective earth) Ground terminals that must be connected to ground prior to establishing any other connections.
	The ground terminals are located on the interior and exterior of the device: Interior ground terminal: potential equalization is connected to the supply network. Exterior ground terminal: device is connected to the plant grounding system.

Communication-specific symbols

Symbol	Meaning
	Wireless Local Area Network (WLAN) Communication via a wireless, local network.
•	LED Light emitting diode is off.
<u> </u>	LED Light emitting diode is on.
	LED Light emitting diode is flashing.

Symbols for certain types of information

Symbol	Meaning
✓	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
X	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
(A)	Reference to documentation
A ⁼	Reference to page
	Reference to graphic
	Visual inspection


Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections
EX	Hazardous area
×	Safe area (non-hazardous area)
≋➡	Flow direction

Function and system design

Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



A002896

- Ue Induced voltage
- B Magnetic induction (magnetic field)
- L Electrode spacing
- I Current
- v Flow velocity

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced (U_e) is proportional to the flow velocity (v) and is supplied to the amplifier by means of two measuring electrodes. The flow volume (Q) is calculated via the pipe cross-section (A). The magnetic field is created through a switched direct current of alternating polarity.

Formulae for calculation

- Induced voltage $U_e = B \cdot L \cdot v$
- Volume flow $Q = A \cdot v$

Measuring system

The device consists of a transmitter and a sensor.

The device is available as a compact version:

The transmitter and sensor form a mechanical unit.

A0026708

Transmitter

Proline 300


Device versions and materials:

- Transmitter housing
- Aluminum, coated: aluminum, AlSi10Mg, coated
- Material of window in transmitter housing: Aluminum, coated: glass


Configuration:

- External operation via 4-line, illuminated graphic local display (LCD) with touch control and guided menus ("Make-it-run" wizards) for application-specific commissioning.
- Via service interface or WLAN interface:
 - Operating tools (e.g. FieldCare, DeviceCare)
 - Web server (access via Web browser, e.g. Microsoft Internet Explorer, Microsoft Edge)

Sensor



Equipment architecture



 \blacksquare 1 Possibilities for integrating measuring devices into a system

- 1 Control system (e.g. PLC)
- 2 Connecting cable (0/4 to 20 mA HART etc.)
- 3 Fieldbus
- 4 Coupler
- 5 Non-hazardous area
- 6 Hazardous area: Zone 2; Class I, Division 2
- 7 Hazardous area: Zone 1; Class I, Division 1

Security

IT security

Our warranty is valid only if the product is installed and used as described in the Operating Instructions. The product is equipped with security mechanisms to protect it against any inadvertent changes to the settings.

IT security measures, which provide additional protection for the product and associated data transfer, must be implemented by the operators themselves in line with their security standards.

Device-specific IT security

The device offers a range of specific functions to support protective measures on the operator's side. These functions can be configured by the user and guarantee greater in-operation safety if used correctly. An overview of the most important functions is provided in the following section:

Function/interface	Factory setting	Recommendation
Write protection via hardware write protection switch $\Rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $	Not enabled	On an individual basis following risk assessment
Access code (also applies for Web server login or FieldCare connection) → 🖺 8	Not enabled (0000)	Assign a customized access code during commissioning
WLAN (order option in display module)	Enabled	On an individual basis following risk assessment
WLAN security mode	Enabled (WPA2- PSK)	Do not change
WLAN passphrase (password) → 🖺 8	Serial number	Assign a customized WLAN passphrase during commissioning
WLAN mode	Access point	On an individual basis following risk assessment
Web server → 🖺 8	Enabled	On an individual basis following risk assessment
CDI-RJ45 service interface → 🗎 9	-	On an individual basis following risk assessment

Protecting access via hardware write protection

Write access to the parameters of the device via the local display, Web browser or operating tool (e.g. FieldCare, DeviceCare) can be disabled via a write protection switch (DIP switch on the main electronics module). When hardware write protection is enabled, only read access to the parameters is possible.

Hardware write protection is disabled when the device is delivered.

Protecting access via a password

Different passwords are available to protect write access to the device parameters or access to the device via the WLAN interface.

- User-specific access code
 - Protect write access to the device parameters via the local display, Web browser or operating tool (e.g. FieldCare, DeviceCare). Access authorization is clearly regulated through the use of a user-specific access code.
- WLAN passphrase
 - The network key protects a connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface which can be ordered as an option.
- Infrastructure mode
 - When the device is operated in infrastructure mode, the WLAN passphrase corresponds to the WLAN passphrase configured on the operator side.

User-specific access code

Write access to the device parameters via the local display, Web browser or operating tool (e.g. FieldCare, DeviceCare) can be protected by the modifiable, user-specific access code.

WLAN passphrase: Operation as WLAN access point

A connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface, which can be ordered as an optional extra, is protected by the network key. The WLAN authentication of the network key complies with the IEEE 802.11 standard.

When the device is delivered, the network key is pre-defined depending on the device. It can be changed via the **WLAN settings** submenu in the **WLAN passphrase** parameter.

Infrastructure mode

A connection between the device and WLAN access point is protected by means of an SSID and passphrase on the system side. Please contact the relevant system administrator for access.

General notes on the use of passwords

- The access code and network key supplied with the device should be changed during commissioning.
- Follow the general rules for generating a secure password when defining and managing the access code or network key.
- The user is responsible for the management and careful handling of the access code and network key.

Access via Web server

The device can be operated and configured via a Web browser with the integrated Web server. The connection is via the service interface (CDI-RJ45) or the WLAN interface. For device versions with the EtherNet/IP and PROFINET communication protocols, the connection can also be established via the terminal connection for signal transmission with EtherNet/IP, PROFINET (RJ45 plug) or PROFINET with Ethernet-APL (two-wire).

The Web server is enabled when the device is delivered. The Web server can be disabled if necessary (e.g. after commissioning) via the **Web server functionality** parameter.

The device and status information can be hidden on the login page. This prevents unauthorized access to the information.

For detailed information on device parameters, see:

Access via OPC-UA

i

The device can communicate with OPC UA clients using the "OPC UA Server" application package.

The OPC UA server integrated in the device can be accessed via the WLAN access point using the WLAN interface - which can be ordered as an optional extra - or the service interface (CDI- RJ45) via Ethernet network. Access rights and authorization as per separate configuration.

The following Security Modes are supported as per the OPC UA Specification (IEC 62541):

- None
- Basic128Rsa15 signed
- Basic128Rsa15 signed and encrypted

Access via service interface (CDI-RJ45)

The device can be connected to a network via the service interface (CDI-RJ45). Device-specific functions quarantee the secure operation of the device in a network.

The use of relevant industrial standards and guidelines that have been defined by national and international safety committees, such as IEC/ISA62443 or the IEEE, is recommended. This includes organizational security measures such as the assignment of access authorization as well as technical measures such as network segmentation.

- Transmitters with an Ex de approval may not be connected via the service interface (CDI-RJ45)!

 Order code for "Approval transmitter + sensor", options (Ex de): BA, BB, C1, C2, GA, GB, MA, MB, NA. NB
- The device can be incorporated into a ring topology. The device is integrated via the terminal connection for signal transmission (output 1) and the connection to the service interface (CDI-RJ45).

Input

Measured variable

Direct measured variables

- Volume flow (proportional to induced voltage)
- Electrical conductivity

Calculated measured variables

Mass flow

Measuring range

Typically v = 0.01 to 10 m/s (0.03 to 33 ft/s) with the specified accuracy

Electrical conductivity: $\geq 5 \mu S/cm$ for liquids in general

Flow characteristic values in SI units: DN 25 to 125 mm (1 to 4 in)

Nominal	diameter	Recommended flow	Factory settings				
		min./max. full scale value (v ~ 0.310 m/s)	Full scale value current output (v ~ 2.5 m/s) Pulse value (~ 2 Pulse/s at v ~ 2.5 m/s)		Low flow cut off (v ~ 0.04 m/s)		
[mm]	[in]	[dm³/min]	[dm³/min] [dm³]		[dm³/min]		
25	1	9 to 300	75	0.5	1		
32	-	15 to 500	125 1		2		
40	1 ½	25 to 700	200 1.5		3		
50	2	35 to 1100	300 2.5		5		
65	_	60 to 2 000	500 5		8		
80	3	90 to 3 000	750 5		12		

Nominal	diameter	Recommended flow	Factory settings				
		min./max. full scale value (v ~ 0.310 m/s)	Full scale value current output (v ~ 2.5 m/s) Pulse value (~ 2 Pulse/s at v ~ 2.5 m/s)		Low flow cut off (v ~ 0.04 m/s)		
[mm]	[in]	[dm³/min]	[dm ³ /min] [dm ³]		[dm³/min]		
100	4	145 to 4700	1200	10	20		
125	-	220 to 7500	1850 15		30		

Flow characteristic values in SI units: DN 150 to 3000 mm (6 to 120 in)

Nominal diameter		Recommended flow	Factory settings		
		min./max. full scale value (v ~ 0.310 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 2 Pulse/s at v ~ 2.5 m/s)	Low flow cut off (v ~ 0.04 m/s)
[mm]	[in]	[m³/h]	[m ³ /h]	[m ³]	[m ³ /h]
150	6	20 to 600	150	0.025	2.5
200	8	35 to 1100	300	0.05	5
250	10	55 to 1700	500	0.05	7.5
300	12	80 to 2 400	750	0.1	10
350	14	110 to 3 300	1000	0.1	15
375	15	140 to 4200	1200	0.15	20
400	16	140 to 4200	1200	0.15	20
450	18	180 to 5 400	1500	0.25	25
500	20	220 to 6600	2 000	0.25	30
600	24	310 to 9600	2 500	0.3	40
700	28	420 to 13 500	3 500	0.5	50
750	30	480 to 15 000	4000	0.5	60
800	32	550 to 18000	4500	0.75	75
900	36	690 to 22 500	6 000	0.75	100
1000	40	850 to 28000	7 000	1	125
-	42	950 to 30 000	8000	1	125
1200	48	1250 to 40 000	10000	1.5	150
-	54	1550 to 50 000	13 000	1.5	200
1400	-	1700 to 55 000	14000	2	225
-	60	1950 to 60 000	16000	2	250
1600	-	2 200 to 70 000	18000	2.5	300
-	66	2 500 to 80 000	20500	2.5	325
1800	72	2 800 to 90 000	23 000	3	350
-	78	3 300 to 100 000	28500	3.5	450
2000	-	3 400 to 110 000	28500	3.5	450
-	84	3 700 to 125 000	31000	4.5	500
2200	-	4100 to 136000	34000	4.5	540
-	90	4300 to 143000	36000	5	570
2400	-	4800 to 162000	40 000	5.5	650

Nominal diameter		Recommended flow	Factory settings		
		min./max. full scale value (v ~ 0.310 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 2 Pulse/s at v ~ 2.5 m/s)	Low flow cut off (v ~ 0.04 m/s)
[mm]	[mm] [in] [[m ³ /h]	[m³]	[m ³ /h]
-	96	5 000 to 168 000	42 000	6	675
_	102	5 700 to 190 000	47 500	7	750
2600	-	5 700 to 191 000	48 000	7	775
-	108	6 500 to 210 000	55 000	7	850
2800	-	6 700 to 222 000	55 500	8	875
-	114	7 100 to 237 000	59 500	8	950
3000	7 600 to 2		63 500	9	1025
_	120	7 900 to 263 000	65 500	9	1050

Flow characteristic values in SI units: DN 50 to 200 mm (2 to 8 in) for order code for "Design", option C "Fixed flange, constricted measuring tube, 0 x DN inlet/outlet runs"

	inal ieter	Recommended flow	Factory settings				
		min./max. full scale value (v ~ 0.125 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 4 Pulse/s at v ~ 2.5 m/s)	Low flow cut off (v ~ 0.01 m/s)		
[mm]	[in]	[dm³/min]	[dm³/min]	[dm³]	[dm³/min]		
50	2	15 to 600	300	1.25	1.25		
65	-	25 to 1000	500	2	2		
80	3	35 to 1500	750	3	3.25		
100	4	60 to 2 400	1200	5	4.75		
125	-	90 to 3 700	1850	8	7.5		
150	6	145 to 5 400	2 500	10	11		
200	8	220 to 9400	5 000	20	19		

Flow characteristic values in SI units: DN 250 to 300 mm (10 to 12 in) for order code for "Design", option C "Fixed flange, constricted measuring tube, $0 \times DN$ inlet/outlet runs"

Nominal Recommended Factory sets				Factory settings	
		min./max. full scale value (v ~ 0.125 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 4 Pulse/s at v ~ 2.5 m/s)	Low flow cut off (v ~ 0.01 m/s)
[mm]	[in]	[m³/h]	[m ³ /h]	[m³]	[m ³ /h]
250	10	20 to 850	500	0.03	1.75
300	12	35 to 1300	750	0.05	2.75

Flow characteristic values in US units: DN 1 to 48 in (25 to 1200 mm)

Nominal	diameter	Recommended flow	Factory settings					
		min./max. full scale value (v ~ 0.310 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 2 Pulse/s at v ~ 2.5 m/s)	Low flow cut off (v ~ 0.04 m/s)			
[in]	[mm]	[gal/min]	[gal/min]	[gal]	[gal/min]			
1	25	2.5 to 80	18	0.2	0.25			
_	32	4 to 130	30	0.2	0.5			
1 1/2	40	7 to 185	50	0.5	0.75			
2	50	10 to 300	75	0.5	1.25			
_	65	16 to 500	130	1	2			
3	80	24 to 800	200	2	2.5			
4	100	40 to 1250	300	2	4			
_	125	60 to 1950	450	5	7			
6	150	90 to 2 650	600	5	12			
8	200	155 to 4850	1200	10	15			
10	250	250 to 7500	1500	15	30			
12	300	350 to 10600	2 400	25	45			
14	350	500 to 15 000	3 600	30	60			
15	375	600 to 19000	4800	50	60			
16	400	600 to 19000	4800	50	60			
18	450	800 to 24 000	6 000	50	90			
20	500	1000 to 30000	7 500	75	120			
24	600	1400 to 44000	10500	100	180			
28	700	1900 to 60000	13500	125	210			
30	750	2 150 to 67 000	16500	150	270			
32	800	2 450 to 80 000	19500	200	300			
36	900	3 100 to 100 000	24000	225	360			
40	1000	3 800 to 125 000	30000	250	480			
42	-	4200 to 135000	33 000	250	600			
48	1200	5 500 to 175 000	42 000	400	600			

Flow characteristic values in US units: DN 54 to 120 in (1400 to 3000 mm)

Nominal	diameter	Recommended flow	Factory settings						
		min./max. full scale value (v ~ 0.310 m/s)	current output (~ 2 Pulse/s at		Low flow cut off (v ~ 0.04 m/s)				
[in]	[mm]	[Mgal/d]	[Mgal/d]	[Mgal]	[Mgal/d]				
54	-	9 to 300	75	0.0005	1.3				
-	1400	10 to 340	85	0.0005	1.3				
60	-	12 to 380	95	0.0005	1.3				
_	1600	13 to 450	110	0.0008	1.7				
66	-	14 to 500	120	0.0008	2.2				
72	1800	16 to 570	140	0.0008	2.6				

Nominal	diameter	Recommended flow	Factory settings						
		min./max. full scale value (v ~ 0.310 m/s)	Full scale value current output (v ~ 2.5 m/s)	Pulse value (~ 2 Pulse/s at v ~ 2.5 m/s)	Low flow cut off (v ~ 0.04 m/s)				
[in]	[mm]	[Mgal/d]	[Mgal/d]	[Mgal]	[Mgal/d]				
78	-	18 to 650	175	0.0010	3.0				
_	2000	20 to 700	175	0.0010	2.9				
84	-	24 to 800	190	0.0011	3.2				
-	2200	26 to 870	210	0.0012	3.4				
90	-	27 to 910	220	0.0013	3.6				
_	2400	31 to 1030	245	0.0014	4.0				
96	-	32 to 1066	265	0.0015	4.0				
102	_	34 to 1203	300	0.0017	5.0				
-	2600	34 to 1212	305	0.0018	5.0				
108	-	35 to 1300	340	0.0020	5.0				
_	2800	42 to 1405	350	0.0020	6.0				
114	_	45 to 1503	375	0.0022 6.0					
_	3000	48 to 1613	405	0.0023 6.0					
120	_	50 to 1665	415	0.0024 7.0					

Flow characteristic values in US units: DN 2 to 12 in (50 to 300 mm) for order code for "Design", option C "Fixed flange, constricted measuring tube, 0 x DN inlet/outlet runs"

	ninal neter	Recommended flow	Factory settings					
		min./max. full scale value (v ~ 0.125 m/s)	Full scale value current output (v ~ 2.5 m/s)	at output (~ 4 Pulse/s at				
[in]	[mm]	[gal/min]	[gal/min]	[gal]	[gal/min]			
2	50	4 to 160	75	0.3	0.35			
-	65	7 to 260	130 0.5		0.6			
3	80	10 to 400	200	0.8	0.8			
4	100	16 to 650	300	1.2	1.25			
-	125	24 to 1000	450	1.8	2			
6	150	40 to 1400	600	2.5	3			
8	200	60 to 2 500	1200	5	5			
10	250	90 to 3 700	1500	6	8			
12	300	155 to 5700	2 400	9	12			

Recommended measuring range

i

Flow limit $\rightarrow \blacksquare 71$

Operable flow range

Over 1000:1

Input signal

Output and input variants

→ 🖺 15

External measured values

To increase the accuracy of certain measured variables or to calculate the mass flow, the automation system can continuously write different measured values to the measuring device:

- Medium temperature enables temperature-compensated conductivity measurement (e.g. iTEMP)
- Reference density for calculating the mass flow
- Various pressure and temperature measuring devices can be ordered from Endress+Hauser: see "Accessories" section $\rightarrow \stackrel{\triangle}{=} 124$

It is recommended to read in external measured values to calculate the corrected volume flow.

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Current input

Digital communication

The measured values can be written by the automation system via:

- FOUNDATION Fieldbus
- PROFIBUS DP
- PROFIBUS PA
- Modbus RS485
- EtherNet/IP
- PROFINET
- PROFINET with Ethernet-APL

Current input 0/4 to 20 mA

Current input	0/4 to 20 mA (active/passive)		
Current span	 4 to 20 mA (active) 0/4 to 20 mA (passive) 		
Resolution 1 μA			
Voltage drop Typically: 0.6 to 2 V for 3.6 to 22 mA (passive)			
Maximum input voltage	≤ 30 V (passive)		
Open-circuit voltage	≤ 28.8 V (active)		
Possible input variables	TemperatureDensity		

Status input

Maximum input values	■ DC -3 to 30 V ■ If status input is active (ON): $R_i > 3 \text{ k}\Omega$				
Response time	Configurable: 5 to 200 ms				
Input signal level	 Low signal: DC -3 to +5 V High signal: DC 12 to 30 V 				
Assignable functions	 Off Reset the individual totalizers separately Reset all totalizers Flow override 				

Output

Output and input variants

Depending on the option selected for output/input 1, different options are available for the other outputs and inputs. Only one option can be selected for each output/input 1 to 3. The following tables must be read vertically (\downarrow) .

Example: If the option BA "4-20 mA HART" was selected for output/input 1, one of the options A, B, D, E, F, H, I or J is available for output 2 and one of the options A, B, D, E, F, H, I or J is available for output 3.

Output/input 1 and options for output/input 2



Options for output/input $3 \rightarrow \triangleq 16$

Order code for "Output; input 1" (020) →		Possible options												
Current output 4 to 20 mA HART	ВА													
Current output 4 to 20 mA HART Ex i passive	1	CA												
Current output 4 to 20 mA HART Ex i active		+	СС											
FOUNDATION Fieldbus			\	SA										
FOUNDATION Fieldbus Ex i				1	TA									
PROFIBUS DP					4	LA								
PROFIBUS PA						\	GA							
PROFIBUS PA Ex i							\	НА						
Modbus RS485								4	MA					
EtherNet/IP 2-port switch integrated									4	NA				
PROFINET 2-port switch integrated										4	RA			
PROFINET with Ethernet-APL											\	RB		
PROFINET with Ethernet-APL Ex i												\	RC	
Order code for "Output; input 2" (021) →	1	4	\	1	4	\								
Not assigned	A	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	
Current output 4 to 20 mA	В			В		В	В		В	В	В	В		
Current output 4 to 20 mA Ex i passive		С	С		С			С					С	
User-configurable input/output 1)	D			D		D	D		D	D	D	D		
Pulse/frequency/switch output	Е			Е		Е	Е		Е	Е	Е	Е		
Double pulse output ²⁾	F								F					
Pulse/frequency/switch output Ex i passive		G	G		G			G					G	
Relay output	Н			Н		Н	Н		Н	Н	Н	Н		
Current input 0/4 to 20 mA	I			I		I	I		I	I	I	I		
Status input	J			J		J	J		J	J	J	J		
						-				•	•			

²⁾ If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for selection for output/input 3 (022).

Output/input 1 and options for output/input 3

Order code for "Output; input 1" (020) →	Possible options												
Current output 4 to 20 mA HART	BA												
Current output 4 to 20 mA HART Ex i passive	4	CA											
Current output 4 to 20 mA HART Ex i active		4	СС										
FOUNDATION Fieldbus			4	SA									
FOUNDATION Fieldbus Ex i				\	TA								
PROFIBUS DP					4	LA							
PROFIBUS PA						4	GA						
PROFIBUS PA Ex i							1	НА					
Modbus RS485								4	MA				
EtherNet/IP 2-port switch integrated									\	NA			
PROFINET 2-port switch integrated										→	RA		
PROFINET with Ethernet-APL											4	RB	
PROFINET with Ethernet-APL Ex i												4	RC
Order code for "Output; input 3" (022) →	\	4	4	\	4	4	1	4	\	→	\	\	4
Not assigned	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α
Current output 4 to 20 mA	В					В			В	В	В	В	
Current output 4 to 20 mA Ex i passive		С	С										
User-configurable input/output	D					D			D	D	D	D	
Pulse/frequency/switch output	Е					E			Е	Е	Е	E	
Double pulse output (slave) 1)	F								F				
Pulse/frequency/switch output Ex i passive		G	G										
Relay output	Н					Н			Н	Н	Н	Н	
Current input 0/4 to 20 mA	I					I			I	I	I	I	
Status input	J					J			J	J	J	J	

¹⁾ If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for output/input 3 (022).

Output signal

Current output 4 to 20 mA HART

Order code	"Output; input 1" (20): Option BA: current output 4 to 20 mA HART
Signal mode	Can be set to: Active Passive
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	250 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Electronics temperature

Current output 4 to 20 mA HART Ex i

Order code	"Output; input 1" (20) choose from: Option CA: current output 4 to 20 mA HART Ex i passive Option CC: current output 4 to 20 mA HART Ex i active
Signal mode	Depends on the selected order version.
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current
Open-circuit voltage	DC 21.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	 250 to 400 Ω (active) 250 to 700 Ω (passive)
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Electronics temperature

FOUNDATION Fieldbus

FOUNDATION Fieldbus	H1, IEC 61158-2, galvanically isolated
Data transfer	31.25 kbit/s

Current consumption	10 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud
Terminating resistor	Integrated, can be activated via DIP switches

PROFIBUS PA

PROFIBUS PA	In accordance with EN 50170 Volume 2, IEC 61158-2 (MBP), galvanically isolated
Data transmission	31.25 kbit/s
Current consumption	10 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

Modbus RS485

Physical interface	RS485 in accordance with EIA/TIA-485 standard
Terminating resistor	Integrated, can be activated via DIP switches

EtherNet/IP

Standards	In accordance with IEEE 802.3
-----------	-------------------------------

PROFINET

Standards	In accordance with IEEE 802.3

PROFINET with Ethernet-APL

Device use	Device connection to an APL field switch The device may only be operated according to the following APL port classifications: If used in hazardous areas: SLAA or SLAC 1) If used in non-hazardous areas: SLAX
	Connection values of APL field switch (corresponds to APL port classification SPCC or SPAA, for instance):
	 Maximum input voltage: 15 V_{DC} Minimum output values: 0.54 W
	Device connection to an SPE switch The device may only be operated according to the following PoDL power class: If used in the non-hazardous area: PoDL power class 10
	Connection values of SPE switch (corresponds to PoDL power class 10, 11 or 12): Maximum input voltage: 30 V _{DC} Minimum output values: 1.85 W
PROFINET	According to IEC 61158 and IEC 61784

18

Ethernet-APL	According to IEEE 802.3cg, APL port profile specification v1.0, galvanically isolated
Data transfer	10 Mbit/s
Current consumption	Transmitter • Max. 400 mA(24 V) • Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)
Permitted supply voltage	9 to 30 V
Network connection	With integrated reverse polarity protection

For more information on using the device in the hazardous area, see the Ex-specific Safety Instructions

Current output 4 to 20 mA

Order code	"Output; input 2" (21), "Output; input 3" (022): Option B: current output 4 to 20 mA
Signal mode	Can be set to: Active Passive
Current span	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current
Maximum output values	22.5 mA
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Electronics temperature

Current output 4 to 20 mA Ex i passive

Order code	"Output; input 2" (21), "Output; input 3" (022): Option C: current output 4 to 20 mA Ex i passive
Signal mode	Passive
Current span	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA Fixed current
Maximum output values	22.5 mA
Maximum input voltage	DC 30 V
Load	0 to 700 Ω
Resolution	0.38 μΑ

Damping	Configurable: 0 to 999 s
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Electronics temperature

Pulse/frequency/switch output

Function	Can be configured as pulse, frequency or switch output
Version	Open collector Can be set to: Active Passive Passive NAMUR Ex-i, passive
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Voltage drop	For 22.5 mA: ≤ DC 2 V
Pulse output	
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Pulse width	Configurable: 0.05 to 2 000 ms
Maximum pulse rate	10 000 Impulse/s
Pulse value	Configurable
Assignable measured variables	 Volume flow Mass flow Corrected volume flow
Frequency output	
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Output frequency	Configurable: end value frequency 2 to $10000Hz(f_{max}=12500Hz)$
Damping	Configurable: 0 to 999.9 s
Pulse/pause ratio	1:1
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Electronics temperature
Switch output	
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Switching behavior	Binary, conductive or non-conductive
Switching delay	Configurable: 0 to 100 s

Number of switching cycles	Unlimited
Assignable functions	 Off On Diagnostic behavior Limit value: Off Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Totalizer 1-3 Electronics temperature Flow direction monitoring Status Empty pipe detection Buildup index HBSI limit value exceeded Low flow cut off

Double pulse output

Function	Double pulse
Version	Open collector Can be set to: Active Passive Passive NAMUR
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Voltage drop	For 22.5 mA: ≤ DC 2 V
Output frequency	Configurable: 0 to 1000 Hz
Damping	Configurable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	 Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Electronics temperature

Relay output

Function	Switch output
Version	Relay output, galvanically isolated
Switching behavior	Can be set to: NO (normally open), factory setting NC (normally closed)

Maximum switching capacity (passive)	■ DC 30 V, 0.1 A ■ AC 30 V, 0.5 A
Assignable functions	 Off On Diagnostic behavior Limit value: Off Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Totalizer 1-3 Electronics temperature Flow direction monitoring Status Empty pipe detection Buildup index HBSI limit value exceeded Low flow cut off

User-configurable input/output

One specific input or output is assigned to a user-configurable input/output (configurable I/O) during device commissioning.

The following inputs and outputs are available for assignment:

- Choice of current output: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Pulse/frequency/switch output
- Choice of current input: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Status input

The technical values correspond to those of the inputs and outputs described in this section.

Signal on alarm

Depending on the interface, failure information is displayed as follows:

HART current output

Device diagnostics	Device condition can be read out via HART Command 48
--------------------	--

PROFIBUS PA

Status and alarm messages	Diagnostics in accordance with PROFIBUS PA Profile 3.02
Failure current FDE (Fault Disconnection Electronic)	0 mA

PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

EtherNet/IP

Device diagnostics	Device condition can be read out in Input Assembly
--------------------	--

PROFINET

Device diagnostics	According to "Application Layer protocol for decentralized periphery", Version 2.3

PROFINET with Ethernet-APL

Device diagnostics	Diagnostics according to PROFINET PA Profile 4
--------------------	--

FOUNDATION Fieldbus

Status and alarm messages	Diagnostics in accordance with FF-891
Failure current FDE (Fault Disconnection Electronic)	0 mA

Modbus RS485

Failure mode	Choose from:
	■ NaN value instead of current value
	■ Last valid value

Current output 0/4 to 20 mA

4 to 20 mA

Failure mode Choose from: 4 to 20 mA in accordance with NAMUR recommendation NE 43 4 to 20 mA in accordance with US Min. value: 3.59 mA Max. value: 22.5 mA Freely definable value between: 3.59 to 22.5 mA Actual value Last valid value	
---	--

0 to 20 mA

Failure mode	Choose from:
	■ Maximum alarm: 22 mA
	■ Freely definable value between: 0 to 20.5 mA

Pulse/frequency/switch output

Pulse output	Pulse output			
Failure mode	Choose from: Actual value No pulses			
Frequency output				
Failure mode Choose from: Actual value 0 Hz Defined value (f max 2 to 12 500 Hz)				
Switch output				
Failure mode	Choose from: Current status Open Closed			

Relay output

Failure mode	Choose from:
	 Current status
	■ Open
	■ Closed

Local display

Plain text display	With information on cause and remedial measures		
Backlight	Red backlighting indicates a device error.		



Status signal as per NAMUR recommendation NE 107

Interface/protocol

- Via digital communication:
 - HART protocol
 - FOUNDATION Fieldbus
 - PROFIBUS PA
 - PROFIBUS DP
 - Modbus RS485
 - EtherNet/IP
 - PROFINET
 - PROFINET with Ethernet-APL
- Via service interface
 - CDI-RJ45 service interface
 - WLAN interface

Plain text display	With information on cause and remedial measures
--------------------	---



Web browser

Plain text display	With information on cause and remedial measures
--------------------	---

Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes		
	The following information is displayed depending on the device version: Supply voltage active Data transmission active Device alarm/error has occurred EtherNet/IP network available EtherNet/IP connection established PROFINET network available PROFINET onnection established PROFINET blinking feature		

Load

Output signal \rightarrow \blacksquare 17

Ex connection data

Safety-related values

Order code for "Output; input 1"	Output type	Safety-related values "Output; input 1"		
		26 (+) 27 (-)		
Option BA	Current output 4 to 20 mA HART	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$		
Option GA	PROFIBUS PA	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$		
Option LA	PROFIBUS DP	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$		
Option MA	Modbus RS485	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$		
Option SA	FOUNDATION Fieldbus	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$		
Option NA	EtherNet/IP	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$		
Option RA	PROFINET	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$		
Option RB	PROFINET with Ethernet- APL	APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30 \ V_{DC}$ $U_M = 250 \ V_{AC}$	2	

Order code for	Output type	Safety-related values			
"Output; input 2"; "Output; input 3"		Output; input 2		Output;	input 3
• / •		24 (+) 25 (-) 22 (+) 23 (-)			23 (-)
Option B	Current output 4 to 20 mA	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	2		
Option D	User-configurable input/ output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	2		
Option E	Pulse/frequency/switch output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	2		
Option F	Double pulse output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	C		
Option H	Relay output	$U_{N} = 30 V_{DC}$ $I_{N} = 100 \text{ mA}_{DC}$ $U_{M} = 250 V_{AC}$			
Option I	Current input 4 to 20 mA	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	3		
Option J	Status input	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm Ad}$	2		

Intrinsically safe values

Order code "Output; input 1"	Output type	Intrinsically safe values "Output; input 1"		
		26 (+)	27 (-)	
Option CA	Current output 4 to 20 mA HART Ex i passive	$\begin{aligned} &U_i = 30 \text{ V} \\ &l_i = 100 \text{ mA} \\ &P_i = 1.25 \text{ W} \\ &L_i = 0 \mu\text{H} \\ &C_i = 6 \text{ nF} \end{aligned}$		
Option CC	Current output 4 to 20 mA HART Ex i active	Ex ia $^{1)}$ $U_0 = 21.8 \text{ V}$ $I_0 = 90 \text{ mA}$ $P_0 = 491 \text{ mW}$ $L_0 = 4.1 \text{ mH (IIC)/15 mH (IIB)}$ $C_0 = 160 \text{ nF (IIC)/}$ 1160 nF (IIB)	Ex ic 2) $U_{0} = 21.8 \text{ V}$ $I_{0} = 90 \text{ mA}$ $P_{0} = 491 \text{ mW}$ $L_{0} = 9 \text{ mH (IIC)/39 mH (IIB)}$ $C_{0} = 600 \text{ nF (IIC)/4000 nF (IIB)}$	
		$\begin{split} &U_{i} = 30 \text{ V} \\ &I_{i} = 10 \text{ mA} \\ &P_{i} = 0.3 \text{ W} \\ &L_{i} = 5 \mu\text{H} \\ &C_{i} = 6 \text{ nF} \end{split}$		
Option HA	PROFIBUS PA Ex i (FISCO Field Device)	$Ex ia ^{1} \\ U_{i} = 30 V \\ I_{i} = 570 mA \\ P_{i} = 8.5 W \\ L_{i} = 10 \mu H \\ C_{i} = 5 nF$	Ex ic 2) $U_{i} = 32 \text{ V}$ $l_{i} = 570 \text{ mA}$ $P_{i} = 8.5 \text{ W}$ $L_{i} = 10 \mu\text{H}$ $C_{i} = 5 \text{ nF}$	
Option TA	FOUNDATION Fieldbus Ex i	$Ex ia ^{1)} \\ U_i = 30 V \\ l_i = 570 mA \\ P_i = 8.5 W \\ L_i = 10 \mu H \\ C_i = 5 nF$	Ex ic 2) $U_{i} = 32 \text{ V}$ $l_{i} = 570 \text{ mA}$ $P_{i} = 8.5 \text{ W}$ $L_{i} = 10 \mu\text{H}$ $C_{i} = 5 \text{ nF}$	
Option RC	PROFINET with Ethernet-APL Ex i	t- Ex ia 1)		

- Only available for Proline 500 transmitter Zone 1; Class I, Division 1. Only available for transmitter Zone 2; Class I, Division 2. 1)

Order code for	Output type	Intrinsically safe values or NIFW values			
"Output; input 2"; "Output; input 3"		Output; input 2		Output;	input 3
		24 (+)	25 (-)	22 (+)	23 (-)
Option C	Current output 4 to 20 mA Ex i passive	$U_{i} = 30 \text{ V}$ $l_{i} = 100 \text{ mA}$ $P_{i} = 1.25 \text{ W}$ $L_{i} = 0$ $C_{i} = 0$			
Option G	Pulse/frequency/switch output Ex i passive	$U_{i} = 30 \text{ V}$ $l_{i} = 100 \text{ mA}$ $P_{i} = 1.25 \text{ W}$ $L_{i} = 0$ $C_{i} = 0$			

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

The outputs are galvanically isolated:
• from the power supply

- from one another
- from the potential equalization (PE) terminal

Protocol-specific data

HART

Manufacturer ID	0x11
Device type ID	0x3C
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω
System integration	Information on system integration: Operating Instructions → 🗎 125. ■ Measured variables via HART protocol ■ Burst Mode functionality

FOUNDATION Fieldbus

Manufacturer ID	0x452B48 (hex)
Ident number	0x103C (hex)
Device revision	1
DD revision	Information and files under:
CFF revision	www.endress.comwww.fieldcommgroup.org
Interoperability Test Kit (ITK)	Version 6.2.0
ITK Test Campaign Number	Information: www.endress.com www.fieldcommgroup.org
Link Master capability (LAS)	Yes
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device
Node address	Factory setting: 247 (0xF7)
Supported functions	The following methods are supported: Restart ENP Restart Diagnostic Set to OOS Set to AUTO Read trend data Read event logbook
Virtual Communication Relation	nships (VCRs)
Number of VCRs	44
Number of link objects in VFD	50
Permanent entries	1
Client VCRs	0
Server VCRs	10
Source VCRs	43
Sink VCRs	0
Subscriber VCRs	43
Publisher VCRs	43

Device Link Capabilities	
Slot time	4
Min. delay between PDU	8
Max. response delay	16
System integration	Information regarding system integration: Operating Instructions → 🗎 125. Cyclic data transmission Description of the modules Execution times Methods

PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x1570
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: ■ https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ https://www.profibus.com
Supported functions	Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Via operating tools (e.g. FieldCare)
Compatibility with earlier model	If the device is replaced, the measuring device Promag 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promag 300 GSD file. Earlier models: Promag 50 PROFIBUS DP ID No.: 1546 (hex) Extended GSD file: EH3x1546.gsd Standard GSD file: EH3_1546.gsd Promag 53 PROFIBUS DP ID No.: 1526 (hex) Extended GSD file: EH3x1526.gsd Standard GSD file: EH3_1526.gsd
	Description of the function scope of compatibility: Operating Instructions → 125.
System integration	Information regarding system integration: Operating Instructions → 🗎 125. Cyclic data transmission Block model Description of the modules

PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x156C
Profile version	3.02

Device description files (GSD, DTM, DD)	Information and files under: ■ https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ https://www.profibus.com
Supported functions	 Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Local display Via operating tools (e.g. FieldCare)
Compatibility with earlier model	If the device is replaced, the measuring device Promag 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promag 300 GSD file.
	Earlier models: Promag 50 PROFIBUS PA ID No.: 1525 (hex) Extended GSD file: EH3x1525.gsd Standard GSD file: EH3_1525.gsd Promag 53 PROFIBUS PA ID No.: 1527 (hex) Extended GSD file: EH3x1527.gsd Standard GSD file: EH3_1527.gsd Description of the function scope of compatibility:
	Operating Instructions → 🗎 125.
System integration	Information regarding system integration: Operating Instructions → 🖺 125. ■ Cyclic data transmission ■ Block model ■ Description of the modules

Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1
Response times	 Direct data access: typically 25 to 50 ms Auto-scan buffer (data range): typically 3 to 5 ms
Device type	Slave
Slave address range	1 to 247
Broadcast address range	0
Function codes	 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers
Broadcast messages	Supported by the following function codes: O6: Write single registers 16: Write multiple registers 23: Read/write multiple registers

Supported baud rate	 1200 BAUD 2400 BAUD 4800 BAUD 9600 BAUD 19200 BAUD 38400 BAUD 57600 BAUD 115200 BAUD 115200 BAUD
Data transfer mode	• 113200 BAOD • ASCII • RTU
Data access	Each device parameter can be accessed via Modbus RS485. For Modbus register information
Compatibility with earlier model	If the device is replaced, the measuring device Promag 300 supports the compatibility of the Modbus registers for the process variables and the diagnostic information with the previous model Promag 53. It is not necessary to change the engineering parameters in the automation system. □ Description of the function scope of compatibility: Operating Instructions → □ 125.
System integration	Information on system integration: Operating Instructions → 🗎 125. • Modbus RS485 information • Function codes • Register information • Response time • Modbus data map

EtherNet/IP

	THE OTDAY A 1 AND A 1 A 1 A 1 A 1 A 1 A 1 A 1 A 1 A 1 A
Protocol	 The CIP Networks Library Volume 1: Common Industrial Protocol The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP
Communication type	■ 10Base-T ■ 100Base-TX
Device profile	Generic device (product type: 0x2B)
Manufacturer ID	0x000049E
Device type ID	0x103C
Baud rates	Automatic ¹⁰ / ₁₀₀ Mbit with half-duplex and full-duplex detection
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Supported CIP connections	Max. 3 connections
Explicit connections	Max. 6 connections
I/O connections	Max. 6 connections (scanner)
Configuration options for measuring device	 DIP switches on the electronics module for IP addressing Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser Electronic Data Sheet (EDS) integrated in the measuring device
Configuration of the EtherNet interface	 Speed: 10 MBit, 100 MBit, auto (factory setting) Duplex: half-duplex, full-duplex, auto (factory setting)
Configuration of the device address	 DIP switches on the electronics module for IP addressing (last octet) DHCP Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser EtherNet/IP tools, e.g. RSLinx (Rockwell Automation)

Device Level Ring (DLR)	Yes
System integration	Information regarding system integration: Operating Instructions $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $
	 Cyclic data transmission Block model Input and output groups

PROFINET

Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.3
Communication type	100 MBit/s
Conformance Class	Conformance Class B
Netload Class	Netload Class 2 0 Mbps
Baud rates	Automatic 100 Mbit/s with full-duplex detection
Cycle times	From 8 ms
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Media Redundancy Protocol (MRP)	Yes
System redundancy support	System redundancy S2 (2 AR with 1 NAP)
Device profile	Application interface identifier 0xF600 Generic device
Manufacturer ID	0x11
Device type ID	0x843C
Device description files (GSD, DTM, DD)	Information and files under: ■ www.endress.com On the product page for the device: Documents/Software → Device drivers ■ www.profibus.com
Supported connections	 2 x AR (IO Controller AR) 1 x AR (IO-Supervisor Device AR connection allowed) 1 x Input CR (Communication Relation) 1 x Output CR (Communication Relation) 1 x Alarm CR (Communication Relation)
Configuration options for measuring device	 DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device. Onsite operation
Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server

Supported functions	 Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM)
System integration	Information regarding system integration: Operating Instructions → 🖺 125. ■ Cyclic data transmission ■ Overview and description of the modules ■ Status coding ■ Startup configuration ■ Factory setting

PROFINET with Ethernet-APL

Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.4			
Communication type	Ethernet Advanced Physical Layer 10BASE-T1L			
Conformance Class	Conformance Class B (PA)			
Netload Class	Netload Class 2 0 Mbps			
Baud rates	10 Mbit/s Full-duplex			
Cycle times	64 ms			
Polarity	Automatic correction of crossed "APL signal +" and "APL signal -" signal lines			
Media Redundancy Protocol (MRP)	Not possible (point-to-point connection to APL field switch)			
System redundancy support	System redundancy S2 (2 AR with 1 NAP)			
Device profile	PROFINET PA profile 4 (Application interface identifier API: 0x9700)			
Manufacturer ID	0x11			
Device type ID	0xA43C			
Device description files (GSD, DTM, FDI)	Information and files under: ■ www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ www.profibus.com			
Supported connections	 2x AR (IO Controller AR) 2x AR (IO Supervisor Device AR connection allowed) 			
Configuration options for measuring device	 DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device. Onsite operation 			
Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server 			

Supported functions	 Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM with FDI package)
System integration	Information regarding system integration: Operating Instructions → 🖺 125. Cyclic data transmission Overview and description of the modules Status coding Startup configuration Factory setting

Power supply

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

Supply	voltage	Input/o	utput 1	Input/o	utput 2	Input/c	output 3
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)
		The termina	The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $				

FOUNDATION Fieldbus

Supply	voltage	Input/o	utput 1	Input/o	utput 2	Input/o	output 3
1 (+)	2 (-)	26 (A)	27 (B)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered → 🖺 15.					

PROFIBUS DP

Supply	voltage	Input/o	output 1	Input/o	utput 2	Input/o	output 3
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $					

PROFIBUS PA

Supply	voltage	Input/o	utput 1	Input/o	utput 2	Input/o	utput 3
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)
		The termina	The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $				

Modbus RS485

Supply	voltage	Input/o	utput 1	Input/o	utput 2	Input/o	utput 3
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered → 🖺 15.					

PROFINET

Supply	voltage	Input/output 1	Input/output 2		Input/o	output 3
1 (+)	2 (-)	PROFINET	24 (+)	25 (-)	22 (+)	23 (-)
		(RJ45 connector)		5	t depends on t rdered → 🖺 1	*

PROFINET with Ethernet-APL

Supply	voltage	Input/output 1	Input/output 2		Input/o	utput 3
1 (+)	2 (-)	PROFINET	24 (+)	25 (-)	22 (+)	23 (-)
		(RJ45 connector)		5	t depends on t rdered → 🖺 1	

EtherNet/IP

Supply	y voltage	Input/output 1	Input/output 2		Input/c	output 3
1 (+)	2 (-)	EtherNet/IP	24 (+)	25 (-)	22 (+)	23 (-)
		(RJ45 connector)			t depends on t rdered → 🖺 1	*

Available device plugs

Provice plugs may not be used in hazardous areas!

Device plugs for fieldbus systems:

Order code for "Input; output 1"

- Option **GA** "PROFIBUS PA" → 🖺 35
- Option **NA** "EtherNet/IP" \rightarrow 🖺 35
- Option **RA** "PROFINET" → 🖺 36
- Option **RB** "PROFINET with Ethernet-APL" → 🖺 36

Device plug for connecting to the service interface:

Order code for "Accessory mounted"

Option **NB**, adapter RJ45 M12 (service interface) $\rightarrow \triangleq 52$

Order code for "Input; output 1", option SA "FOUNDATION Fieldbus"

Order code for	Cable entry/connection → 🗎 37			
"Electrical connection"	2	3		
M, 3, 4, 5	7/8" connector	-		

Order code for "Input; output 1", option GA "PROFIBUS PA"

Order code for	Cable entry/connection → 🗎 37			
"Electrical connection"	2	3		
L, N, P, U	Connector M12 × 1	-		

Order code for "Input; output 1", option NA "EtherNet/IP"

Order code for	Cable entry/connection → 🖺 37	
"Electrical connection"	2	3
L, N, P, U	Connector M12 × 1	-
R ^{1) 2)} , S ^{1) 2)} , T ^{1) 2)} , V ^{1) 2)}	Connector M12 × 1	Connector M12 × 1

Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001

2) Suitable for integrating the device in a ring topology.

Order code for "Input; output 1", option RA "PROFINET"

Order code for	Cable entry/connection → 🖺 37	
"Electrical connection"	2 3	
L, N, P, U	Connector M12 × 1	_
R ¹⁾²⁾ , S ¹⁾²⁾ , T ¹⁾²⁾ , V ¹⁾²⁾	Connector M12 × 1	Connector M12 × 1

- Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001.
- 2) Suitable for integrating the device in a ring topology.

Order code for "Input; output 1", option RB "PROFINET with Ethernet-APL"

Order code	Cable entry/connection → 🗎 37	
"Electrical connection"	2	3
L, N, P, U	M12 plug × 1	-

Order code for "Accessory mounted", option NB "Adapter RJ45 M12 (service interface)"

Order code	Cable entry/coupling → 🗎 37	
"Accessory mounted"	Cable entry 2	Cable entry 3
NB	Plug M12 × 1	-

Supply voltage

Order code for "Power supply"	Terminal voltage		Frequency range
Option D	DC 24 V	±20%	-
Option E	AC 100 to 240 V	-15 to +10%	50/60 Hz, ±4 Hz
Option I	DC 24 V	±20%	-
	AC 100 to 240 V	-15 to +10%	50/60 Hz, ±4 Hz

Power consumption

Transmitter

Max. 10 W (active power)

switch-on current	Max. 36 A (<5 ms) as per NAMUR Recommendation NE 21
-------------------	---

Current consumption

Transmitter

- Max. 400 mA (24 V)
- Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)

Power supply failure

- Totalizers stop at the last value measured.
- Depending on the device version, the configuration is retained in the device memoryor in the pluggable data memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

Overcurrent protection element

The device must be operated with a dedicated circuit breaker, as it does not have an ON/OFF switch of its own.


- The circuit breaker must be easy to reach and labeled accordingly.
- Permitted nominal current of the circuit breaker: 2 A up to maximum 10 A.

Electrical connection

Transmitter connection



- Terminal assignment → 🗎 34
 - Device plugs available → 🖺 35



A002678

- 1 Terminal connection for supply voltage
- 2 Terminal connection for signal transmission, input/output
- 3 Terminal connection for signal transmission, input/output or terminal for network connection via service interface (CDI-RJ45); Optional: terminal connection for external WLAN antenna or connection for remote display and operating module DKX001
- 4 Terminal connection for potential equalization (PE)
- An adapter for the RJ45 to the M12 plug is optionally available:
 Order code for "Accessories", option **NB**: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can therefore be established via an M12 plug without opening the device.


Connecting in a ring topology

Device versions with EtherNet/IP and PROFINET communication protocols can be integrated into a ring topology. The device is integrated via the terminal connection for signal transmission (output 1) and the connection to the service interface (CDI-RJ45).



Integrate the transmitter into a ring topology:

- EtherNet/IP
- PROFINET




A0026781

- 1 Terminal connection for supply voltage
- 2 Terminal connection for signal transmission: PROFINET or EtherNet/IP (RJ45 connector)
- 3 Terminal connection to service interface (CDI-RJ45)
- 4 Terminal connection for potential equalization (PE)

If the device has additional inputs/outputs, these are routed in parallel via the cable entry for connection to the service interface (CDI-RJ45).

Connecting the remote display and operating module DKX001


- The remote display and operating module DKX001 is available as an optional extra $\rightarrow \triangleq 122$.
- The measuring device is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring device. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring device display module. Only one display or operation unit may be connected to the transmitter at any one time.




- 1 Remote display and operating module DKX001
- 2 Terminal connection for potential equalization (PE)
- 3 Connecting cable
- Measuring device
- Terminal connection for potential equalization (PE)

Connection examples

Current output 4 to 20 mA HART




- **₽** 2 Connection example for 4 to 20 mA HART current output (active)
- Automation system with current input (e.g. PLC) 1
- Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications $\rightarrow \implies 52$
- Connection for HART operating devices $\rightarrow \blacksquare 107$
- Resistor for HART communication ($\geq 250~\Omega$): observe maximum load $\rightarrow ~ riangleq 17$ 4
- 5 Analog display unit: observe maximum load $\rightarrow \square 17$
- Transmitter



- \blacksquare 3 Connection example for 4 to 20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- Analog display unit: observe maximum load → 17
- 5 Transmitter


HART input



■ 4 Connection example for HART input with a common negative (passive)

- 1 Automation system with HART output (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 5 Pressure transmitter (e.g. Cerabar M, Cerabar S): see requirements
- 6 Transmitter


PROFIBUS PA



A00287

- 5 Connection example for PROFIBUS PA
- 1 Control system (e.g. PLC)
- 2 PROFIBUS PA segment coupler
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line


PROFIBUS DP



 \blacksquare 6 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2


- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter
- If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

EtherNet/IP




- **№** 7 ${\it Connection\ example\ for\ Ether Net/IP}$
- Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- Transmitter

EtherNet/IP: DLR (Device Level Ring)



- Control system (e.g. PLC)
- 2 Ethernet switch
- 3 *Observe cable specifications* \rightarrow $\stackrel{\triangle}{=}$ 52
- Transmitter
- Connecting cable between the two transmitters


PROFINET



₽8 ${\it Connection\ example\ for\ PROFINET}$


- Control system (e.g. PLC)
- 2 Ethernet switch
- Observe cable specifications
- 4 Device plug
- Transmitter

PROFINET with Ethernet-APL



- **9** ${\it Connection example for PROFINET with Ethernet-APL}$
- 1 Cable shield
- 2 Measuring device
- 3 Local grounding
- Potential equalization
 Trunk or TCP
- 5
- Field switch

PROFINET: MRP (Media Redundancy Protocol)




A0027544

- Control system (e.g. PLC) Ethernet switch
- 2
- 3 *Observe cable specifications* $\rightarrow \implies 52$
- Transmitter 4
- ${\it Connecting\ cable\ between\ the\ two\ transmitters}$

42


PROFINET: system redundancy S2



■ 10 Connection example for system redundancy S2

- Control system 1 (e.g. PLC)
- Synchronization of control systems 2
- Control system 2 (e.g. PLC)
- Industrial Ethernet Managed Switch 4
- Transmitter


FOUNDATION Fieldbus



■ 11 Connection example for FOUNDATION Fieldbus


- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus) 2
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- T-box
- Measuring device
- Local grounding 6
- Bus terminator
- Potential matching line

Modbus RS485




- \blacksquare 12 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2
- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter

Current output 4-20 mA



A002875


- 13 Connection example for 4-20 mA current output (active)
- 1 Automation system with current input (e.g. PLC)
- 2 Analog display unit: observe maximum load $\rightarrow \square$ 17
- 3 Transmitter



A0028759


- 14 Connection example for 4-20 mA current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Analog display unit: observe maximum load $\rightarrow \blacksquare 17$
- 4 Transmitter

Pulse/frequency output



- 15 Connection example for pulse/frequency output (passive)
- Automation system with pulse/frequency input (e.g. PLC with 10 kΩ pull-up or pull-down resistor)
- 2 Power supply
- *3 Transmitter: observe input values* → **2** *20*


Switch output



■ 16 Connection example for switch output (passive)

- Automation system with switch input (e.g. PLC with a 10 kΩ pull-up or pull-down resistor)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \triangleq 20$

Double pulse output




■ 17 Connection example for double pulse output (active)

- Automation system with double pulse input (e.g. PLC)
- 2 Transmitter: observe input values $\rightarrow \stackrel{\square}{=} 21$
- 3 Double pulse output
- 4 Double pulse output (slave), phase-shifted

Endress+Hauser 45


.....



■ 18 Connection example for double pulse output (passive)

- 1 Automation system with double pulse input (e.g. PLC with a 10 $k\Omega$ pull-up or pull-down resistor)
- 2 Power supply
- 4 Double pulse output
- 5 Double pulse output (slave), phase-shifted


Relay output



■ 19 Connection example for relay output (passive)

- 1 Automation system with relay input (e.g. PLC)
- 2 Power supply


Current input



■ 20 Connection example for 4 to 20 mA current input

- 1 Power supply
- 2 Terminal box
- 3 External measuring device (to read in pressure or temperature, for instance)
- 4 Transmitter

Status input



A0028764

■ 21 Connection example for status input

- Automation system with status output (e.g. PLC)
- 2 Power supply
- 3 Transmitter

Potential equalization

Introduction

Correct potential equalization (equipotential bonding) is a prerequisite for stable and reliable flow measurement. Inadequate or incorrect potential equalization can result in device failure and present a safety hazard.

The following requirements must be observed to ensure correct, trouble-free measurement:

- The principle that the medium, the sensor and the transmitter must be at the same electrical potential applies.
- Take in-company grounding guidelines, materials and the grounding conditions and potential conditions of the pipe into consideration.
- The necessary potential equalization connections must be established using a ground cable with a minimum cross-section of 6 mm² (0.0093 in²) and a cable lug.
- In the case of remote device versions, the ground terminal in the example always refers to the sensor and not to the transmitter.
- You can order accessories such as ground cables and ground disks directly from Endress+Hauser
 → 🖺 122
- For devices intended for use in hazardous areas, observe the instructions in the Ex documentation (XA).

Abbreviations used

- PE (Protective Earth): potential at the protective earth terminals of the device
- P_P (Potential Pipe): potential of the pipe, measured at the flanges
- P_M (Potential Medium): potential of the medium


Connection examples for standard situations

Unlined and grounded metal pipe

- $\ \ \, \blacksquare$ Potential equalization is via the measuring pipe.
- The medium is set to ground potential.

Starting conditions:

- Pipes are correctly grounded on both sides.
- Pipes are conductive and at the same electrical potential as the medium



A0044854


► Connect the connection housing of the transmitter or sensor to ground potential by means of the ground terminal provided for this purpose.

Metal pipe without liner

- Potential equalization is via the ground terminal and pipe flanges.
- The medium is set to ground potential.

Starting conditions:

- Pipes are not sufficiently grounded.
- Pipes are conductive and at the same electrical potential as the medium



A0042089


- 1. Connect both sensor flanges to the pipe flange via a ground cable and ground them.
- 2. Connect the connection housing of the transmitter or sensor to ground potential by means of the ground terminal provided for this purpose.
- 3. For DN ≤ 300 (12"): Mount the ground cable directly on the conductive flange coating of the sensor with the flange screws.
- 4. For DN ≥ 350 (14"): Mount the ground cable directly on the metal transport bracket. Observe the screw tightening torques: see the Brief Operating Instructions for the sensor.

Plastic pipe or pipe with insulating liner

- Potential equalization is via the ground terminal and ground disks.
- The medium is set to ground potential.

Starting conditions:

- The pipe has an insulating effect.
- Low-impedance medium grounding close to the sensor is not guaranteed.
- $\ \ \, \blacksquare$ Equalizing currents through the medium cannot be ruled out.



0044856

- 1. Connect the ground disks to the ground terminal of the transmitter or sensor connection housing via the ground cable.
- 2. Connect the connection to ground potential.

Connection example with the potential of medium not equal to protective ground without the "Floating measurement" option


In these cases, the medium potential can differ from the potential of the device.

Metal, ungrounded pipe

The sensor and transmitter are installed in a way that provides electrical insulation from PE, e.g. applications for electrolytic processes or systems with cathodic protection.

Starting conditions:

- Unlined metal pipe
- Pipes with an electrically conductive liner



40042252

- 1. Connect the pipe flanges and transmitter via the ground cable.
- 2. Route the shielding of the signal lines via a capacitor (recommended value 1.5µF/50V).
- 3. Device connected to power supply such that it is floating in relation to the protective earth (isolation transformer). This measure is not required in the case of 24V DC supply voltage without PE (= SELV power unit).

Connection examples with the potential of medium not equal to protective ground with the "Floating measurement" option

In these cases, the medium potential can differ from the potential of the device.

Introduction

The "Floating measurement" option enables the galvanic isolation of the measuring system from the device potential. This minimizes harmful equalizing currents caused by differences in potential between the medium and the device. The "Floating measurement" option is optionally available: order code for "Sensor option", option CV

Operating conditions for the use of the "Floating measurement" option

Device version	Compact version and remote version (length of connecting cable $\leq 10 \ m)$
Differences in voltage between medium potential and device potential	As small as possible, usually in the mV range
Alternating voltage frequencies in the medium or at ground potential (PE)	Below typical power line frequency in the country



To achieve the specified conductivity measuring accuracy, a conductivity calibration is recommended when the device is installed.


A full pipe adjustment is recommended when the device is installed.

Plastic pipe

Sensor and transmitter are correctly grounded. A difference in potential can occur between the medium and protective earth. Potential equalization between P_M and PE via the reference electrode is minimized with the "Floating measurement" option.

Starting conditions:

- The pipe has an insulating effect.
- Equalizing currents through the medium cannot be ruled out.



A0044855


- 1. Use the "Floating measurement" option, while also observing the operating conditions for floating measurement.
- 2. Connect the connection housing of the transmitter or sensor to ground potential by means of the ground terminal provided for this purpose.

Metal, ungrounded pipe with insulating liner

The sensor and transmitter are installed in a way that provides electrical insulation from PE. The medium and pipe have different potentials. The "Floating measurement" option minimizes harmful equalizing currents between $P_{\rm M}$ and $P_{\rm P}$ via the reference electrode.

Starting conditions:

- Metal pipe with insulating liner
- Equalizing currents through the medium cannot be ruled out.



A0044857

- 1. Connect the pipe flanges and transmitter via the ground cable.
- 2. Route the shielding of the signal cables via a capacitor (recommended value $1.5\mu F/50V$).
- 3. Device connected to power supply such that it is floating in relation to the protective earth (isolation transformer). This measure is not required in the case of 24V DC supply voltage without PE (= SELV power unit).
- 4. Use the "Floating measurement" option, while also observing the operating conditions for floating measurement.

Terminals

Spring-loaded terminals: Suitable for strands and strands with ferrules. Conductor cross-section 0.2 to 2.5 $\,\mathrm{mm^2}$ (24 to 12 AWG).

Cable entries

- Cable gland: M20 \times 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
 - NPT ½"
 - G ½"
 - M20

50

Pin assignment, device plug

FOUNDATION Fieldbus

	Pin		Assignment	Coding	Plug/socket
2 3	1	+	Signal +	A	Plug
1 4	2	-	Signal –		
	3		Grounding		
	4		Not assigned		

PROFIBUS PA

	Pin		Assignment	Coding	Plug/socket
2 / 3	1	+	PROFIBUS PA +	A	Plug
1 4	2		Grounding		
	3	-	PROFIBUS PA -		
	4		Not assigned		

- Recommended plug:
 Binder, series 713, part no. 99 1430 814 04
 - Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

PROFINET

2	Pin		Assignment
	1	+	TD +
1 3	2	+	RD +
	3	-	TD -
	4	-	RD -
4 A0032047	Cod	ling	Plug/socket
	I)	Socket

- Recommended plug:
 Binder, series 825, part no. 99 3729 810 04
 - Phoenix, part no. 1543223 SACC-M12MSD-4Q

PROFINET with Ethernet-APL


	Pin		Assignment	Coding	Plug/socket
3 4	1	-	APL signal -	A	Socket
2 1	2	+	APL signal +		
	3		Cable shield ¹		
	4		Not assigned		
	Metal plug housing		Cable shield		
	¹ If a cable shield is used				



Recommended plug:

- Binder, series 713, part no. 99 1430 814 04
- Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

EtherNet/IP




Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q

Service interface

Order code for "Accessories mounted", option NB: Adapter RJ45 M12 (service interface)





Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q

Cable specification

Permitted temperature range

- The installation guidelines that apply in the country of installation must be observed.
- The cables must be suitable for the minimum and maximum temperatures to be expected.

Power supply cable (incl. conductor for the inner ground terminal)

Standard installation cable is sufficient.

Protective grounding cable for the outer ground terminal

Conductor cross-section < 2.1 mm² (14 AWG)

The use of a cable lug enables the connection of larger cross-sections.

The grounding impedance must be less than 2 Ω .

Signal cable

Current output 4 to 20 mA HART

A shielded cable is recommended. Observe grounding concept of the plant.

PROFIBUS PA

Twisted, shielded two-wire cable. Cable type A is recommended.

For further information on planning and installing PROFIBUS networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz
Cable capacitance	< 30 pF/m
Wire cross-section	> 0.34 mm ² (22 AWG)
Cable type	Twisted pairs
Loop resistance	≤110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.



For further information on planning and installing PROFIBUS networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.



For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization

PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.



For more information on planning and installing PROFINET networks, see: "PROFINET Cabling and Interconnection Technology", Guideline for PROFINET

PROFINET with Ethernet-APL

The reference cable type for APL segments is fieldbus cable type A, MAU type 1 and 3 (specified in IEC 61158-2). This cable meets the requirements for intrinsically safe applications according to IEC TS 60079-47 and can also be used in non-intrinsically safe applications.

Cable type	A
Cable capacitance	45 to 200 nF/km
Loop resistance	15 to 150 Ω/km
Cable inductance	0.4 to 1 mH/km

Further details are provided in the Ethernet-APL Engineering Guideline (https://www.ethernet-apl.org).

FOUNDATION Fieldbus

Twisted, shielded two-wire cable.



For further information on planning and installing FOUNDATION Fieldbus networks see:

- Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)
- FOUNDATION Fieldbus Guideline
- IEC 61158-2 (MBP)

Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz
Cable capacitance	< 30 pF/m
Wire cross-section	> 0.34 mm ² (22 AWG)
Cable type	Twisted pairs
Loop resistance	≤110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.

Current output 0/4 to 20 mA

Standard installation cable is sufficient

Pulse /frequency /switch output

Standard installation cable is sufficient

Double pulse output

Standard installation cable is sufficient

Relay output

Standard installation cable is sufficient.

Current input 0/4 to 20 mA

Standard installation cable is sufficient

Status input

Standard installation cable is sufficient

Connecting cable for transmitter - remote display and operating module DKX001 $\,$

Standard cable

A standard cable can be used as the connecting cable.

Standard cable	4 cores (2 pairs); pair-stranded with common shield
Shielding	Tin-plated copper-braid, optical cover ≥ 85 %
Capacitance: core/shield	Maximum 1000 nF for Zone 1; Class I, Division 1
L/R	Maximum 24 μ H/ Ω for Zone 1; Class I, Division 1
Cable length	Maximum 300 m (1000 ft), see the following table

Cross-section	Cable length for use in: Non-hazardous area Hazardous area: Zone 2; Class I, Division 2 Hazardous area: Zone 1; Class I, Division 1
0.34 mm ² (22 AWG)	80 m (270 ft)
0.50 mm ² (20 AWG)	120 m (400 ft)
0.75 mm ² (18 AWG)	180 m (600 ft)

Cross-section	Cable length for use in: Non-hazardous area Hazardous area: Zone 2; Class I, Division 2 Hazardous area: Zone 1; Class I, Division 1	
1.00 mm ² (17 AWG)	240 m (800 ft)	
1.50 mm ² (15 AWG)	300 m (1000 ft)	

Optionally available connecting cable

Standard cable	$2\times2\times0.34~\text{mm}^2$ (22 AWG) PVC cable $^{1)}$ with common shield (2 pairs, pair-stranded)
Flame resistance According to DIN EN 60332-1-2	
Oil-resistance	According to DIN EN 60811-2-1
Shielding	Tin-plated copper-braid, optical cover \geq 85 %
Capacitance: core/shield	≤200 pF/m
L/R	<24 μH/Ω
Available cable length	10 m (35 ft)
Operating temperature	When mounted in a fixed position: -50 to $+105$ °C (-58 to $+221$ °F); when cable can move freely: -25 to $+105$ °C (-13 to $+221$ °F)

UV radiation can impair the cable outer sheath. Protect the cable from direct sunshine where possible.

Overvoltage protection

Mains voltage fluctuations	→ 🖺 36	
Overvoltage category	Overvoltage category II	
Short-term, temporary overvoltage	Up to 1200 V between cable and ground, for max. 5 s	
Long-term, temporary overvoltage	Up to 500 V between cable and ground	

Performance characteristics

Reference operating conditions

- Error limits following DIN EN 29104, in future ISO 20456
- Water, typically: +15 to +45 °C (+59 to +113 °F); 0.5 to 7 bar (73 to 101 psi)
- Data as indicated in the calibration protocol
- Accuracy based on accredited calibration rigs according to ISO 17025


Maximum measured error

o.r. = of reading

Error limits under reference operating conditions

Volume flow


- \bullet ±0.5 % o.r. ± 1 mm/s (0.04 in/s)
- \bullet Optional: ± 0.2 % o.r. \pm 2 mm/s (0.08 in/s)
- Fluctuations in the supply voltage do not have any effect within the specified range.



■ 22 Maximum measured error in % o.r.

Flat Spec

In the case of Flat Spec, the measured error is constant in the range from $v_{0.5}$ ($v_{0.2}$) to v_{max} .



■ 23 Flat Spec in % o.r.

Flat Spec flow values 0.5 %

Nominal	diameter	v _{0.5}		v _{0.5} v _{max}	
[mm]	[in]	[m/s]	[ft/s]	[m/s]	[ft/s]
25 to 600	1 to 24	0.5	1.64	10	32
50 to 300 ¹⁾	2 to 12	0.25	0.82	5	16

1) Order code for "Design", option C

Flat Spec flow values 0.2 %

Nominal	minal diameter $\mathbf{v}_{0.2}$ \mathbf{v}_{\max}		v _{0.2}		ıax
[mm]	[in]	[m/s]	[ft/s]	[m/s]	[ft/s]
25 to 600	1 to 24	1.5	4.92	10	32
50 to 300 ¹⁾	2 to 12	0.6	1.97	4	13

1) Order code for "Design", option C


Electrical conductivity

The values apply for:


- Devices installed in a metal pipe or in a non-metal pipe with ground disks
- Devices whose potential equalization was performed according to the instructions in the associated Operating Instructions
- Measurements at a reference temperature of 25 °C (77 °F). At different temperatures, attention
 must be paid to the temperature coefficient of the medium (typically 2.1 %/K)

Conductivity [µS/cm]	Measured error [%] of reading
5 to 20	± 20%
> 20 to 50	± 10%
> 50 to 10 000	 Standard: ± 10% Optional ¹⁾: ± 5%
> 10 000 to 20 000	± 10%
> 20 000 to 100 000	± 20%

1) Order code for "Calibrated conductivity measurement", option CW



■ 24 Measured error (standard)



■ 25 Measured error (optional: order code for "Calibrated conductivity measurement", option CW)

Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

Pulse/frequency output

o.r. = of reading

Accuracy	Max. ±50 ppm o.r. (over the entire ambient temperature range)
----------	---

Repeatability

o.r. = of reading

Volume flow

Max. ± 0.1 % o.r. \pm 0.5 mm/s (0.02 in/s)

Electrical conductivity

Max. ±5 % o.r.

Influence of ambient temperature

Current output

Temperature coefficient	Max. 1 μΑ/°C
-------------------------	--------------


Pulse/frequency output

Temperature coefficient No additional effect. Included in accuracy.	
--	--

Installation


Mounting location

- Do not install the device at the highest point of the pipe.
- Do not install the device upstream from a free pipe outlet in a down pipe.



A0042131


The device should ideally be installed in an ascending pipe.



A004231

Installation near valves

Install the device in the direction of flow upstream from the valve.




Installation upstream from a down pipe

NOTICE

Negative pressure in the measuring pipe can damage the liner!

- ▶ If installing upstream of down pipes whose length $h \ge 5$ m (16.4 ft): install a siphon with a vent valve downstream of the device.
- ho This arrangement prevents the flow of liquid stopping in the pipe and air entrainment.




A0028981

- 1 Vent valve
- 2 Pipe siphon
- h Length of down pipe

Installation with partially filled pipes

- Partially filled pipes with a gradient require a drain-type configuration.
- The installation of a cleaning valve is recommended.



A004108


ho No inlet and outlet runs for devices with the order code for "Design": Option C, H or I.

Installation near pumps

NOTICE

Negative pressure in the measuring pipe can damage the liner!

- ▶ In order to maintain the system pressure, install the device in the flow direction downstream from the pump.
- ▶ Install pulsation dampers if reciprocating, diaphragm or peristaltic pumps are used.



A004108

- i
- Information on the measuring system's resistance to vibration and shock \rightarrow $\stackrel{\square}{=}$ 66

Installation of very heavy devices


Support required for nominal diameters of DN \geq 350 mm (14 in).

NOTICE

Damage to the device!

If incorrect support is provided, the sensor housing could buckle and the internal magnetic coils could be damaged.

▶ Only provide supports at the pipe flanges.



A0041087


Installation in event of pipe vibrations

A remote version is recommended in the event of strong pipe vibrations.

NOTICE

Pipe vibrations can damage the device!

- ▶ Do not expose the device to strong vibrations.
- ► Support the pipe and fix it in place.
- ▶ Support the device and fix it in place.
- Mount the sensor and transmitter separately.



Orientation


The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

Orien	Recommendation	
Vertical orientation	↑	
Horizontal orientation, transmitter at top	A0015589	1)
Horizontal orientation, transmitter at bottom	A0015590	2) 3) × 4)
Horizontal orientation, transmitter at side	A0015592	×

- 1) Applications with low process temperatures may reduce the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.
- 2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.
- 3) To prevent the electronics from overheating in the event of strong heat formation (e.g. CIP or SIP cleaning process), install the device with the transmitter part pointing downwards.
- When the empty pipe detection function is switched on, empty pipe detection only works if the transmitter housing is pointing upwards.


Vertical

Optimum for self-emptying pipe systems and for use in conjunction with empty pipe detection.



Horizontal

- Ideally, the measuring electrode plane should be horizontal. This prevents brief insulation of the measuring electrodes by entrained air bubbles.
- Empty pipe detection only works if the transmitter housing is pointing upwards as otherwise there is no guarantee that the empty pipe detection function will actually respond to a partially filled or empty measuring tube.



A0029344

- 1 EPD electrode for empty pipe detection
- 2 Measuring electrodes for signal detection
- 3 Reference electrode for potential equalization

Inlet and outlet runs


Installation with inlet and outlet runs

Installation requires inlet and outlet runs: devices with the order code for "Design", option D, E, F and G.


Installation with elbows, pumps or valves

To avoid a vacuum and to maintain the specified level of accuracy, if possible install the device upstream from assemblies that produce turbulence (e.g. valves, T-sections) and downstream from pumps.

 $\label{lem:maintain} \mbox{Maintain straight, unimpeded inlet and outlet runs.}$



A002899



A004213

Installation without inlet and outlet runs

Depending on the device design and installation location, the inlet and outlet runs can be reduced or omitted entirely.



Maximum measured error

When the device is installed with the inlet and outlet runs described, a maximum measured error of ± 0.5 % of the reading ± 1 mm/s (0.04 in/s) can be quaranteed.


Devices and possible order options

Order code for "Design"			
Option	Description	Design	
С	Fixed flange, constricted measuring tube, 0 x DN inlet/outlet runs	Constricted measuring tube ¹⁾	
Н	Lap joint flange, 0 x DN inlet/outlet runs	Full Bore ²⁾	
I	Fixed flange, 0 x DN inlet/outlet runs		
J	Fixed flange, short installed length, 0 x DN inlet/outlet runs		
К	Fixed flange, long installed length, 0 x DN inlet/outlet runs		

- "Constricted measuring tube" stands for a reduction of the internal diameter of the measuring tube. The reduced internal diameter causes a higher flow velocity inside the measuring tube.
- 2) "Full Bore" stands for the full diameter of the measuring tube. There is no pressure loss with a full diameter.

Installation before or after bends

Installation without inlet and outlet runs is possible: devices with the order code for "Design", option C, H, I, J and K.




Installation downstream of pumps

Installation without inlet and outlet runs is possible: devices with the order code for "Design", option C, H and I.



In the case of devices with the order code for "Design", option J and K, an inlet run of only $\geq 2 \times DN$ must be taken into consideration.




Installation upstream of valves

Installation without inlet and outlet runs is possible: devices with the order code for "Design", option C, H and I.

i

In the case of devices with the order code for "Design", option J and K, an outlet run of only ≥ 1 x DN must be taken into consideration.




Installation downstream of valves

Installation without inlet and outlet runs is possible if the valve is 100% open during operation: devices with the order code for "Design", option C, H and I.



In the case of devices with the order code for "Design", option J and K, an inlet run of only ≥ 2 x DN must be taken into consideration if the valve is 100% open during operation.




Adapters

Suitable adapters to DIN EN 545 (double-flange reducers) can be used to install the sensor in larger-diameter pipes. The resultant increase in the rate of flow improves measuring accuracy with very slow-moving fluids.

The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders:

- Calculate the ratio of the diameters d/D.
- From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.
- The nomogram only applies to liquids with a viscosity similar to that of water.




A0029002

64

Special mounting instructions

Weather protection cover



■ 26 Engineering unit mm (in)


Environment

Ambient temperature range

Transmitter	Standard: -40 to +60 °C (-40 to +140 °F)
Local display	-20 to $+60$ °C (-4 to $+140$ °F), the readability of the display may be impaired at temperatures outside the temperature range.
Sensor	 Process connection material, carbon steel: 10 to +60 °C (+14 to +140 °F) Process connection material, stainless steel: 40 to +60 °C (-40 to +140 °F)
Liner	Do not exceed or fall below the permitted temperature range of the liner .

If operating outdoors:

- Install the measuring device in a shady location.
- Avoid direct sunlight, particularly in warm climatic regions.
- Avoid direct exposure to weather conditions.



Storage temperature

The storage temperature corresponds to the operating temperature range of the transmitter and the sensor $\rightarrow \blacksquare 65$.

- Protect the measuring device against direct sunlight during storage in order to avoid unacceptably high surface temperatures.
- Select a storage location where moisture cannot collect in the measuring device as fungus or bacteria infestation can damage the liner.
- If protection caps or protective covers are mounted these should never be removed before installing the measuring device.

Relative humidity

The device is suitable for use in outdoor and indoor areas with a relative humidity of 4 to 95%.

Operating height

According to EN 61010-1

- ≤ 2000 m (6562 ft)
- > 2000 m (6562 ft) with additional overvoltage protection (e.g. Endress+Hauser HAW Series)

Degree of protection

Transmitter

- IP66/67, Type 4X enclosure, suitable for pollution degree 4
- When the housing is open: IP20, Type 1 enclosure, suitable for pollution degree 2
- Display module: IP20, Type 1 enclosure, suitable for pollution degree 2

Optional

Order code for "Sensor option", option C3

- IP66/67, type 4X enclosure
- Fully welded, with protective coating as per EN ISO 12944 C5-M
- For the operation of the device in corrosive environments

External WLAN antenna

IP67

Vibration- and shock-resistance

Sinusoidal vibration according to IEC 60068-2-6

- 2 to 8.4 Hz, 3.5 mm peak
- 8.4 to 2000 Hz, 1 g peak

Vibration broad-band random, according to IEC 60068-2-64

- 10 to 200 Hz, 0.003 g²/Hz
- 200 to 2000 Hz, 0.001 g²/Hz
- Total: 1.54 g rms

Shock half-sine, according to IEC 60068-2-27

6 ms 30 g

Rough handling shocks according to IEC 60068-2-31

Mechanical load

Transmitter housing:

- Protect against mechanical effects, such as shock or impact
- Do not use as a ladder or climbing aid


Electromagnetic compatibility (EMC)

- As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)
- Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170
 Volume 2, IEC 61784
- The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.
- Details are provided in the Declaration of Conformity.
- This unit is not intended for use in residential environments and cannot guarantee adequate protection of the radio reception in such environments.

Process

Medium temperature range

- 0 to +80 °C (+32 to +176 °F) for hard rubber, DN 50 to 3000 (2 to 120")
- \bullet –20 to +50 °C (–4 to +122 °F) for polyurethane, DN 25 to 1200 (1 to 48")
- -20 to +90 °C (-4 to +194 °F) for PTFE, DN 25 to 300 (1 to 12")



 T_A Ambient temperature

T_F Medium temperature

Colored area: The ambient temperature range of -10 to -40 °C (+14 to -40 °F) and the medium temperature range of -10 to -20 °C (+14 to -4 °F) only apply for stainless flanges


Conductivity

 $\geq \! 5~\mu S/cm$ for liquids in general.

Pressure/temperature ratings

The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.

Process connection: fixed flange according to EN 1092-1 (DIN 2501)




 \blacksquare 27 Process connection material: stainless steel (-20 $^{\circ}$ C (-4 $^{\circ}$ F)); carbon steel (-10 $^{\circ}$ C (14 $^{\circ}$ F))


Endress+Hauser 67

A0038122-E

Process connection: fixed flange according to ASME B16.5




■ 28 Process connection material: stainless steel




■ 29 Process connection material: carbon steel

Process connection: fixed flange according to JIS B2220




■ 30 Process connection material: stainless steel ($-20 \,^{\circ}\text{C}$ ($-4 \,^{\circ}\text{F}$)); carbon steel ($-10 \,^{\circ}\text{C}$ ($14 \,^{\circ}\text{F}$))

Process connection: fixed flange according to AWWA C207




Process connection material: carbon steel

Process connection: fixed flange according to AS 2129



Process connection material: carbon steel

Process connection: fixed flange according to AS 4087




Process connection material: carbon steel

69 Endress+Hauser

A0038128-EN

Process connection: lap joint flange/lap joint flange, stamped plate according to EN 1092-1 (DIN 2501) and ASME B16.5; DN 25 to 300 (1 to 12")



 \blacksquare 34 Process connection material: stainless steel (-20 °C (-4 °F)); carbon steel (-10 °C (14 °F))

- 1 Lap joint flange PN16/ Class150
- 2 Lap joint flange, stamped plate PN10, lap joint flange PN10

Pressure tightness

Liner: hard rubber

Nominal diameter		Limit values for absolute pressure in [mbar] ([psi]) for medium temperatures:		
[mm]	[in]	+25 °C (+77 °F)	+50 °C (+122 °F)	+80 °C (+176 °F)
50 3000	2 120	0 (0)	0 (0)	0 (0)

Liner: polyurethane

Nominal diameter		Limit values for absolute pressure in [mbar] ([psi]) for medium temperatures:	
[mm]	[in]	+25 °C (+77 °F)	+50 ℃ (+122 °F)
25 1200	1 48	0 (0)	0 (0)

Liner: PTFE

Nominal diameter		Limit values for absolute pressure in [mbar] ([psi]) for medium temperatures:	
[mm]	[in]	+25 °C (+77 °F)	+90 °C (+194 °F)
25	1	0 (0)	0 (0)
40	2	0 (0)	0 (0)
50	2	0 (0)	0 (0)
65	2 1/2	0 (0)	40 (0.58)
80	3	0 (0)	40 (0.58)
100	4	0 (0)	135 (2.0)
125	5	135 (2.0)	240 (3.5)
150	6	135 (2.0)	240 (3.5)
200	8	200 (2.9)	290 (4.2)
250	10	330 (4.8)	400 (5.8)
300	12	400 (5.8)	500 (7.3)


Flow limit

The diameter of the pipe and the flow rate determine the nominal diameter of the sensor. The optimum velocity of flow is between 2 to 3 m/s (6.56 to 9.84 ft/s). Also match the velocity of flow (v) to the physical properties of the medium:


- v < 2 m/s (6.56 ft/s): for abrasive media (e.g. potter's clay, lime milk, ore slurry)
- v > 2 m/s (6.56 ft/s): for media producing buildup (e.g. wastewater sludge)
- A necessary increase in the flow velocity can be achieved by reducing the sensor nominal diameter.
- For an overview of the full scale values for the measuring range, see the "Measuring range" section

Pressure loss

- No pressure loss occurs if the sensor is installed in a pipe with the same nominal diameter.
- Pressure losses for configurations incorporating adapters according to DIN EN 545 \Rightarrow \triangleq 64



■ 35 Pressure loss DN 50 to 80 (2 to 3") for order code for "Design", option C "Fixed flange, constricted measuring tube", 0 x DN inlet/outlet runs"



■ 36 Pressure loss DN 100 to 300 (4 to 12") for order code for "Design", option C "Fixed flange, constricted measuring tube", 0 x DN inlet/outlet runs"

Endress+Hauser 71

A0032667-EN

System pressure

Installation near pumps $\rightarrow \implies 59$


Thermal insulation

If process fluids are very hot, it is necessary to insulate pipes in order to reduce energy loss and to prevent individuals from accidentally coming into contact with hot pipes. Please observe the applicable standards and guidelines for insulating pipes.

A WARNING

Electronics overheating on account of thermal insulation!

► The housing support is used for heat dissipation and must be completely free (i.e. uncovered). At the very maximum, the sensor insulation may extend as far as the upper edge of the two sensor half-shells.




A002121

Vibrations

Installation in event of pipe vibrations $\rightarrow \triangleq 60$

Magnetism and static electricity



A004215

■ 37 Avoid magnetic fields

Custody transfer mode

The measuring device is optionally tested in accordance with OIML R49 and has an EU type-examination certificate according to Measuring Instruments Directive 2014/32/EU for service subject to legal metrological control ("custody transfer") for cold water (Annex III).

The permitted medium temperature in these applications is 0 to +50 °C (+32 to +122 °F).

The device is used with a legally controlled totalizer on the local display and optionally with legally controlled outputs.

Measuring devices subject to legal metrological control totalize in both directions, i.e. all the outputs consider flow components in the positive (forward) and negative (reverse) flow direction.

Generally a measuring device subject to legal metrological control is secured against tampering by seals on the transmitter or sensor. These seals may normally only be opened by a representative of the competent authority for legal metrology controls.


After putting the device into circulation or after sealing the device, operation is only possible to a limited extent.

Detailed ordering information is available from your local Endress+Hauser sales center for national approvals (outside Europe) as cold water meters based on OIML R49.

Mechanical construction

Dimensions in SI units

Compact version



A0033783

Order code for "Housing", option A "Aluminum, coated"

A 1)	B 1)	С	G 2)	Н	I 2)
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
169	68	101	200	59	141

- 1) Depending on the cable gland used: values up to + 30 mm
- 2) For version without local display: values 30 mm

Order code for "Housing", option A "Aluminum, coated"; Ex d or XP

A 1)	В	С	G ²⁾	Н	I
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
188	85	103	217	58	159

- 1) Depending on the cable gland used: values up to + 30 mm
- 2) For version without local display: values 40 mm

DN 25 to 300 mm (1 to 12 in): Sensor with aluminum half-shell housing

DN	I			Ore	der code	for "Desi	gn"				
			Options	D, E, H, I			Opti	on C			
		D 1)	E 1) 2) 3)	F 1) 2) 3)	M 1)	D 1)	E 1) 2) 3)	F 1) 2) 3)	M 1)	К	L
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
25	1	84	271	355	120	-	-	-	-	4)	200
32	-	84	271	355	120	-	-	-	-	4)	200
40	1 ½	84	271	355	120	-	-	-	-	4)	200
50	2	84	271	355	120	84	271	355	120	4)	200
65	-	109	296	405	180	84	271	355	120	4)	200
80	3	109	296	405	180	84	271	355	120	4)	200
100	4	109	296	405	180	109	296	405	180	4)	250
125	-	150	336	486	260	109	296	405	180	4)	250
150	6	150	336	486	260	109	296	405	180	4)	300
200	8	180	361	541	324	150	336	486	260	4)	350
250	10	205	386	591	400	150	336	486	260	4)	450
300	12	230	411	641	460	180	361	541	324	4)	500

- 1) The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) $\bar{\text{With}}$ order code for "Sensor option", option CG "Sensor extended neck for insulation": values + 110 mm
- 3) For Ex d or XP versions: values + 30 mm
- 4) Depends on the liner \rightarrow \blacksquare 101

DN 25 to 300 mm (1 to 12 in): Sensor with fully welded carbon steel housing

DN	J			Or	der code	for "Desig	jn"				
			Opti	on E			Opti	on C			
		$\begin{array}{ c c c c c c c c c c c c c c c c c c c$					K	L			
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
25	1	70	290	360	140	-	-	-	-	3)	200
32	-	70	290	360	140	-	-	-	-	3)	200
40	1 ½	70	290	360	140	-	-	-	-	3)	200
50	2	70	290	360	140	70	290	360	140	3)	200
65	-	82	302	384	165	70	290	360	140	3)	200
80	3	87	307	394	175	70	290	360	140	3)	200
100	4	100	320	420	200	82	302	384	165	3)	250
125	-	113	333	446	226	87	307	394	175	3)	250
150	6	134	354	488	269	100	320	420	200	3)	300
200	8	160	380	540	320	113	333	446	226	3)	350

DN	I			Or	der code	for "Desig	jn"				
		Option C Option C									
		D 1)	$D^{1)} \mid E^{1 2 } \mid F^{1 2 } \mid M^{1 } \mid D^{1 } \mid E^{1 2 } \mid F^{1 2 } \mid M^{1 }$					К	L		
[mm]	[in]	[mm] [mm] [mm] [mm] [mm] [mm]					[mm]	[mm]	[mm]	[mm]	
250	10	193	413	606	387	134	354	488	269	3)	450
300	12	218	438	656	437	160	380	540	320	3)	500

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) With order code for "Sensor option", option CG "Sensor extended neck for insulation": values + 110 mm
- 3) Depends on the liner $\rightarrow = 101$

DN 350 to 400 mm (14 to 16 in)

			Order code	for "Design"			
			Option	ns E, I			
D	N	D ¹⁾ E ²⁾ F M			К	L	
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
350	14	282	462	744	564	3)	550
375	15	308	488	796	616	3)	600
400	16	308	488	796	616	3)	600

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) For Ex d or XP versions: values + 30 mm

DN 450 to 900 mm (18 to 36 in)

				Ord	er code	for "Des	ign"					
			Optio	ns F, J			Option	ns G, K				
D	DN $D^{(1)} \mid E^{(1)(2)} \mid F^{(1)(2)} \mid$		M 1)	$D^{1)} \mid E^{1) 2)} \mid F^{1) 2)} \mid M^{1)}$		M 1)	K		L			
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[n	nm]
450	18	290	475	765	580	333	518	851	666	3)	600 ⁴⁾	650 ⁵⁾
500	20	315	500	815	630	359	544	903	717	3)	600 ⁴⁾	650 ⁵⁾
600	24	365	550	915	730	411	596	1007	821	3)	600 ⁴⁾	780 ⁵⁾
700	28	426	611	1037	851	512	697	1209	1024	3)	700 ⁴⁾	910 ⁵⁾
750	30	463	648	1111	926	512	697	1209	1024	3)	750 ⁴⁾	975 ⁵⁾
800	32	482	667	1149	964	534	719	1253	1065	3)	800 4)	1040 5)
900	36	532	717	1249	1064	610	795	1405	1218	3)	900 ⁴⁾	1 170 ⁵⁾

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) For Ex d or XP versions: values + 30 mm
- 3) Depends on the liner \rightarrow \blacksquare 101
- 4) Order code for "Design", option F "Fixed flange, short installed length" and option J "Fixed flange, short installed length, 0 x DN inlet/outlet runs"
- 5) Order code for "Design", option G "Fixed flange, long installed length" and option K "Fixed flange, long installed length 0 x DN inlet/outlet runs"

DN 1000 to 2000 mm (40 to 78 in)

			Order code	for "Design"				
			Options	F, G, J, K				
D	N	D 1)	E 1) 2)	F 1) 2)	M 1)	К	L	
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[m	m]
1000	40	582	767	1349	1164	3)	10004)	1300 ⁵⁾
-	42	618	803	1421	1236	3)	1050 ⁴⁾	1365 ⁵⁾
1200	48	696	881	1577	1392	3)	12004)	1560 ⁵⁾
_	54	809	994	1803	1617	3)	1350 ⁴⁾	1755 ⁵⁾
1400	-	809	994	1803	1617	3)	1 400 ⁴⁾	1820 ⁵⁾
-	60	909	1094	2 003	1817	3)	1500 ⁴⁾	1950 ⁵⁾
1600	-	909	1094	2 003	1817	3)	1600 ⁴⁾	2 080 ⁵⁾
-	66	960	1145	2 105	1919	3)	1650 ⁴⁾	2 145 ⁵⁾
1800	72	1016	1201	2217	2 032	3)	1800 ⁴⁾	2 340 ⁵⁾
-	78	1127	1312	2 439	2254	3)	2 000 4)	2 600 ⁵⁾
2000	-	1127	1312	2 439	2 2 5 4	3)	2 000 4)	2 600 ⁵⁾

- 1) The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) For Ex d or XP versions: values + 30 mm
- 3) Depends on the liner $\rightarrow \blacksquare 101$
- 4) Order code for "Design", option F "Fixed flange, short installed length" and option J "Fixed flange, short installed length, 0 x DN inlet/outlet runs"
- 5) Order code for "Design", option G "Fixed flange, long installed length" and option K "Fixed flange, long installed length $0 \times 10 \times 10^{-5}$ x DN inlet/outlet runs"


DN 2200 to 3000 mm (84 to 120 in)

			Order code	for "Design"			
			Optio	n F, J			
D	N	D 1)	E 1) 2)	F 1)	M 1)	К	L
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
-	84	1227	1412	2 639	2 454	3)	2 200
2200	-	1227	1412	2 639	2 454	3)	2 200
-	90	1332	1517	2 849	2 6 6 4	3)	2 400
2400	-	1332	1517	2 849	2 6 6 4	3)	2 400
-	96	1431	1616	3 047	2861	3)	2 450
-	102	1516	1701	3217	3 0 3 2	3)	2 600
2600	-	1 442	1627	3 0 6 9	2883	3)	2 600
-	108	1602	1787	3 389	3204	3)	2 750
2800	-	1547	1732	3 2 7 9	3 093	3)	2 800
-	114	1688	1873	3 5 6 1	3375	3)	2 900
3000	-	1647	1832	3 479	3 2 9 3	3)	3 000
-	120	1774	1959	3 733	3 5 4 7	3)	3 050

- 1) The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) For Ex d or XP versions: values + 30 mm
- 3) Depends on the liner \rightarrow $\stackrel{\triangle}{=}$ 101

Flange connections

Fixed flange



DN	A	В	С	D	E	L
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm
350	490	445	12 × Ø22	22	1)	2)
400	540	495	16 × Ø22	22		
450	595	565	20 × Ø26	22		
500	645	600	20 × Ø22	24		
600	755	705	20 × Ø26	30		
700	860	810	24 × Ø26	30		
800	975	920	24 × Ø30	30		
900	1075	1020	24 × Ø30	34		
1000	1175	1120	28 × Ø30	38		
1200	1405	1340	32 × Ø33	42		
1400	1630	1560	36 × Ø36	56		
1600	1830	1760	40 × Ø36	63		
1800	2 0 4 5	1970	44 × Ø39	69		
2000	2 2 6 5	2 180	48 × Ø42	74		
2200	2 475	2390	52 × Ø42	81		
2400	2 685	2 600	56 × Ø42	87		
2600	2 905	2810	60 × Ø48	91		
2800	3 1 1 5	3 0 2 0	64 × Ø48	101		
3000	3315	3220	68 × Ø48	102		

Depends on the liner $\rightarrow \boxminus 101$ Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water) $\rightarrow \boxminus 73$ 1) 2)

Carbon steel:	order code for "P	rocess connection	2501 / DIN 2512N) on", option D2K tion", option D2S	: PN 10		
DN	A	В	С	D	E	L
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
200	340	295	8 × Ø22	24	1)	2)
250	395	350	12 × Ø22	26		
300	445	400	12 × Ø22	26		
350	505	460	16 × Ø22	26		
400	565	515	16 × Ø26	26		
450	615	565	20 × Ø26	28		
500	670	620	20 × Ø26	28		
600	780	725	20 × Ø30	30		
700	895	840	24 × Ø30	35		
800	1015	950	24 × Ø33	38		
900	1115	1050	28 × Ø33	38		
1000	1230	1160	28 × Ø36	44		
1200	1455	1380	32 × Ø39	55		
1400	1675	1590	36 × Ø42	65		
1600	1915	1820	40 × Ø48	75		
1800	2 115	2 020	44 × Ø48	85		
2000	2325	2 2 3 0	48 × Ø48	90		
2200	2 5 5 0	2 440	52 × Ø56	100		
2400	2760	2 650	56 × Ø56	110		
2600	2960	2850	60 × Ø56	110		
2800	3 180	3 0 7 0	64 × Ø56	124		
3000	3 405	3 2 9 0	68 × Ø62	132		
Surface roughr	ness (flange): EN	N 1092-1 Form	B1 (DIN 2526 Form	C), Ra 6.3 to 12	5 μm	

- 1) Depends on the liner \rightarrow \blacksquare 101

Carbon steel:	Flange in accordance with EN 1092-1 (DIN 2501 / DIN 2512N): PN 16 Carbon steel: order code for "Process connection", option D3K Stainless steel: order code for "Process connection", option D3S										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
65	185	145	8 × Ø18	20	1)	2)					
80	200	160	8 × Ø18	20							
100	220	180	8 × Ø18	22							
125	250	210	8 × Ø18	24							
150	285	240	8 × Ø22	24							
200	340	295	12 × Ø22	26							
250	405	355	12 × Ø26	32							
300	460	410	12 × Ø26	32							
350	520	470	16 × Ø26	30							

Carbon steel:	Flange in accordance with EN 1092-1 (DIN 2501 / DIN 2512N): PN 16 Carbon steel: order code for "Process connection", option D3K Stainless steel: order code for "Process connection", option D3S							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]		
400	580	525	16 × Ø30	32				
450	640	585	20 × Ø30	34				
500	715	650	20 × Ø33	36				
600	840	770	20 × Ø36	40				
700	910	840	24 × Ø36	40				
800	1025	950	24 × Ø39	41				
900	1125	1050	28 × Ø39	48				
1000	1255	1170	28 × Ø42	59				
1200	1485	1390	32 × Ø48	78				
1400	1685	1590	36 × Ø48	84				
1600	1930	1820	40 × Ø56	102				
1800	2 130	2 0 2 0	44 × Ø56	110				
2000	2345	2230	48 × Ø62	124				
Surface rough	ness (flange): EN	N 1092-1 Form	B1 (DIN 2526 Form	C), Ra 6.3 to 12				

- 1) Depends on the liner \rightarrow $\stackrel{\triangle}{=}$ 101

Carbon steel:	Flange in accordance with EN 1092-1 (DIN 2501 / DIN 2512N): PN 25 Carbon steel: order code for "Process connection", option D4K Stainless steel: order code for "Process connection", option D4S							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]		
200	360	310	12 × Ø26	32	1)	2)		
250	425	370	12 × Ø30	36				
300	485	430	16 × Ø30	40				
350	555	490	16 × Ø33	38				
400	620	550	16 × Ø36	40				
450	670	600	20 × Ø36	46				
500	730	660	20 × Ø36	48				
600	845	770	20 × Ø39	48				
700	960	875	24 × Ø42	50				
800	1085	990	24 × Ø48	53				
900	1185	1090	28 × Ø48	57				
1000	1320	1210	28 × Ø56	63				
Surface rough	ness (flange): EN	N 1092-1 Form	B1 (DIN 2526 Form	C), Ra 6.3 to 12	2.5 µm			

Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water) → 🖺 73

Flange in accordance with EN 1092-1 (DIN 2501 / DIN 2512N): PN 40 Carbon steel: order code for "Process connection", option D5K Stainless steel: order code for "Process connection", option D5S						
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
25	115	85	4 × Ø14	16	1)	2)
32	140	100	4 × Ø18	18		
40	150	110	4 × Ø18	18		
50	165	125	4 × Ø18	20		
65	185	145	8 × Ø18	24		
80	200	160	8 × Ø18	26		
100	235	190	8 × Ø22	26		
125	270	220	8 × Ø26	28		
150	300	250	8 × Ø26	30		
Surface roughn	iess (flange): EN	1092-1 Form I		n C), Ra 6.3 to 12	2.5 µm	

- 1) Depends on the liner \rightarrow \blacksquare 101

Carbon steel	Flange according to ASME B16.5, Class 150 Carbon steel: order code for "Process connection", option A1K Stainless steel: order code for "Process connection", option A1S									
D	N	A B C D			D	Е	L			
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]			
25	1	108	79.2	4 × Ø16	12.6	1)	2)			
40	1 ½	127	98.6	4 × Ø16	15.9					
50	2	152.4	120.7	4 × Ø19.1	17.5					
80	3	190.5	152.4	4 × Ø19.1	22.3					
100	4	228.6	190.5	8 × Ø19.1	22.3					
150	6	279.4	241.3	8 × Ø22.4	23.8					
200	8	342.9	298.5	8 × Ø22.4	26.8					
250	10	406.4	362	12 × Ø25.4	29.6					
300	12	482.6	431.8	12 × Ø25.4	30.2					
350	14	535	476.3	12 × Ø28.6	35.4					
400	16	595	539.8	16 × Ø28.6	37					
450	18	635	577.9	16 × Ø31.8	40.1					
500	20	700	635	20 × Ø31.8	43.3					
600	24	815	749.3	20 × Ø34.9	48.1					
Surface rough	hness (flange):	Ra 6.3 to 12.5	μm							

- 1) Depends on the liner \rightarrow \bigcirc 101

Flange according to ASME B16.5, Class 300 Carbon steel: order code for "Process connection", option A2K Stainless steel: order code for "Process connection", option A2S									
D	N	A	В	С	D	E	L		
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]		
25	1	123.9	88.9	4 × Ø19.1	15.9	1)	2)		
40	1 ½	155.4	114.3	4 × Ø22.4	19				
50	2	165.1	127	8 × Ø19.1	20.8				
80	3	209.6	168.1	8 × Ø22.4	26.8				
100	4	254	200.2	8 × Ø22.4	30.2				
150	6	317.5	269.7	12 × Ø22.4	35				
Surface rough	nness (flange):	Ra 6.3 to 12.5	μm				•		

1) 2)

Carbon steel:	,	Process connecti	ion", option N3K ction", option N3S			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
50	155	120	4 × Ø19	16	1)	2)
65	175	140	4 × Ø19	18		
80	185	150	8 × Ø19	18		
100	210	175	8 × Ø19	18		
125	250	210	8 × Ø23	20		
150	280	240	8 × Ø23	22		
200	330	290	12 × Ø23	22		
250	400	355	12 × Ø25	24		
300	445	400	16 × Ø25	24		
Surface roughi	ness (flange): R	a 6.3 to 12.5 μr	n			

Depends on the liner $\rightarrow~ binom{1}{2}$ 101

1) 2)

Flange accord Carbon steel: Stainless stee						
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
25	125	90	4 × Ø19	16	1)	2)
32	135	100	4 × Ø19	18		
40	140	105	4 × Ø19	18		
50	155	120	8 × Ø19	18		
65	175	140	8 × Ø19	20		
80	200	160	8 × Ø23	22		
100	225	185	8 × Ø23	24		

Carbon steel:	Flange according to JIS B2220, 20K Carbon steel: order code for "Process connection", option N4K Stainless steel: order code for "Process connection", option N4S								
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
125	270	225	8 × Ø25	26					
150	305	260	12 × Ø25	28					
200	350	305	12 × Ø25	30					
250	430	380	12 × Ø27	34					
300	480	430	16 × Ø27	36					
Surface rough	ness (flange): R	a 6.3 to 12.5 μr	n						

- 1)
- 2)

D	N	Α	В	C	D	E	L
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
700	28	927	863.6	28 × Ø35	33.4	1)	2)
750	30	984	914.4	28 × Ø35	35.0		
800	32	1060	977.9	28 × Ø42	38.1		
900	36	1168	1085.9	32 × Ø42	41.3		
1000	40	1289	1200.2	36 × Ø42	41.3		
-	42	1346	1257.3	36 × Ø42	44.5		
1200	48	1511	1422.4	44 × Ø42	47.7		
-	54	1683	1593.9	44 × Ø48	54.0		
-	60	1855	1759.0	52 × Ø48	57.2		
-	66	2 032	1930.4	52 × Ø48	63.5		
1800	72	2 197	2 095.5	60 × Ø48	66.7		
-	78	2 362	2 260.6	64 × Ø54	69.9		
-	84	2 535	2 425.7	64 × Ø54	73.1		
-	90	2 705	2717.8	68 × Ø60	76.2		
-	96	2877	2 755.9	68 × Ø60.3	82.55		
-	102	3 048	2 908.3	68 × Ø66.7	82.55		
-	108	3219	3 067.0	68 × Ø66.7	85.73	1	
-	114	3391	3219.5	68 × Ø73	88.90	1	
_	120	3 5 6 2	3371.8	68 × Ø73	88.90	1	

- 1)
- 2)


	ding to AS 2129 r "Process connec		2K			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
80	185	146	4 × Ø18	12	1)	2)
100	215	178	8 × Ø18	13		
150	280	235	8 × Ø22	17		
200	335	292	8 × Ø22	19		
250	405	356	12 × Ø22	22		
300	455	406	12 × Ø26	25		
350	525	470	12 × Ø26	30		
400	580	521	12 × Ø26	32		
450	640	584	16 × Ø26	35		
500	705	641	16 × Ø26	38		
600	825	756	16 × Ø33	48		
700	910	845	20 × Ø33	51		
750	995	927	20 × Ø36	54		
800	1060	984	20 × Ø36	54	1	
900	1175	1092	24 × Ø36	64	1	
1000	1255	1 175	24 × Ø39	67	1	
1200	1490	1410	32 × Ø39	79	1	
urface rough	ness (flange): R	a 6.3 to 12.5 μι	n	'	1	

- 1) Depends on the liner \rightarrow \bigcirc 101

	ling to AS 4087 "Process connec		зк			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
80	185	146	4 × Ø18	12	1)	2)
100	215	178	4 × Ø18	13		
150	280	235	8 × Ø18	13		
200	335	292	8 × Ø18	19		
250	405	356	8 × Ø22	19		
300	455	406	12 × Ø22	23		
350	525	470	12 × Ø26	30		
375	550	495	12 × Ø26	30		
400	580	521	12 × Ø26	32		
450	640	584	12 × Ø26	30		
500	705	641	16 × Ø26	38		
600	825	756	16 × Ø30	48		
700	910	845	20 × Ø30	56		
750	995	927	20 × Ø33	56		
800	1060	984	20 × Ø36	56		

Flange according to AS 4087, PN 16 Order code for "Process connection", option M3K								
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]		
900	1175	1092	24 × Ø36	66				
1000	1255	1175	24 × Ø36	66				
1200	1490	1410	32 × Ø36	76				
Surface roughi	ness (flange): R	a 6.3 to 12.5 μr	n					

Lap joint flange



A003786

Carbon ste	Lap joint flange in accordance with EN 1092-1 (DIN 2501 / DIN 2512N): PN 10 Carbon steel: order code for "Process connection", option D22 Stainless steel: order code for "Process connection", option D24												
DN A B C D E F L													
[mm] [in] [mm] [mm] [mm] [mm] [mm]													
200	8	340	295	8 × Ø22	24	264	1)	2)					
250	10	395	350	12 × Ø22	26	317							
300	300 12 445 400 12 × Ø22 26 367												
Surface rou	ghness (flan	ge): Ra 6.3 to	12.5 um										

Carbon ste	Lap joint flange in accordance with EN 1092-1 (DIN 2501 / DIN 2512N): PN 16 Carbon steel: order code for "Process connection", option D32 Stainless steel: order code for "Process connection", option D34													
D	N	A	В	С	D	E	F	L						
[mm]	[in]	[in] [mm] [mm] [mm] [mm] [mm] [mm]												
25	1	115	85	4 × Ø14	16	49	1)	2)						
32	-	140	100	4 × Ø18	18	65								
40	1 1/2	150	110	4 × Ø18	18	71								
50	2	165	125	4 × Ø18	20	88								
65	-	185	145	8 × Ø18	20	103								
80	3	200	160	8 × Ø18	20	120								

Carbon ste	el: order cod	e for "Process	connection",	(DIN 2501 A , option D32 n", option D3		N): PN 16							
D	N	A	В	С	D	E	F	L					
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]					
100	4	220	180	8 × Ø18	22	148							
125	-	250	210	8 × Ø18	22	177							
150	6	285	240	8 × Ø22	24	209							
200	8	340	295	12 × Ø22	26	264							
250	10	405	355	12 × Ø26	29	317							
300	300 12 460 410 12 × Ø26 32 367												
Surface rou	ghness (flan	ge): Ra 6.3 to	o 12.5 um										


1) 2)

Carbon ste	Lap joint flange according to ASME B16.5, Class 150 Carbon steel: order code for "Process connection", option A12 Stainless steel: order code for "Process connection", option A14													
D	N	A	В	С	D	E	F	L						
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]						
25	1	110	80	4 × Ø16	14	49	1)	2)						
40 1 ½ 125 98 4 × Ø16 17.5 71														
50	2	150	121	4 × Ø19	19	88								
80	3	190	152	4 × Ø19	24	120								
100	4	230	190	8 × Ø19	24	148								
150	6	280	241	8 × Ø23	25	209								
200	8	345	298	8 × Ø23	29	264								
250	10	405	362	12 × Ø25	30	317								
300	12	485	432	12 × Ø25	32	378								
Surface rou	ghness (flan	ge): Ra 6.3 to	o 12.5 µm											

1)

2)

Lap joint flange, stamped plate



Carbon stee	Lap joint flange, stamped plate in accordance with EN 1092-1 (DIN 2501 / DIN 2512N): PN 10 Carbon steel: order code for "Process connection", option D21 Stainless steel: order code for "Process connection", option D23													
DN	A	В	С	D	E	F	L							
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]							
25	115	85	4 x Ø13.5	16.5	49	1)	2)							
32	140	100	4 x Ø17.5	17	65									
40	150	110	4 x Ø17.5	16.5	71									
50	165	125	4 x Ø17.5	18.5	88									
65	185	145	4 x Ø17.5	20	103									
80	200	160	8 x Ø17.5	23.5	120									
100	220	180	8 x Ø17.5	24.5	148									
125	250	210	8 x Ø17.5	24	177									
150	285	240	8 x Ø21.5	25	209									
200	340	295	8 x Ø21.5	27.5	264									
250	405	350	12 x Ø21.5	30.5	317									
300	445	400	12 x Ø21.5	34.5	367									
Surface roug	hness (flange)	: Ra 6.3 to 12	.5 μm											


Accessories

External WLAN antenna

i

The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



■ 38 Engineering unit mm (in)


External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/reception conditions at the transmitter mounting location are poor.



■ 39 Engineering unit mm (in)

Ground disks for flange connections




D	N	Pressure rating	1	A	1	В]	D	1	Н
[mm]	[inch]		[mm]	[inch]	[mm]	[inch]	[mm]	[inch]	[mm]	[inch]
25	1"	1)	26	1.02	62	2.44	77.5	3.05	87.5	3.44
32	1 1/4"	1)	35	1.38	80	3.15	87.5	3.44	94.5	3.72
40	1 1/2"	1)	41	1.61	82	3.23	101	3.98	103	4.06
50	2"	1)	52	2.05	101	3.98	115.5	4.55	108	4.25
65	2 1/2"	1)	68	2.68	121	4.76	131.5	5.18	118	4.65
80	3"	1)	80	3.15	131	5.16	154.5	6.08	135	5.31
100	4"	1)	104	4.09	156	6.14	186.5	7.34	153	6.02
125	5"	1)	130	5.12	187	7.36	206.5	8.13	160	6.30
150	6"	1)	158	6.22	217	8.54	256	10.08	184	7.24
200	8"	1)	206	8.11	267	10.51	288	11.34	205	8.07
250	10"	1)	260	10.2	328	12.91	359	14.13	240	9.45
300	12"	PN 10 PN 16 Cl. 150	312	12.3	375	14.76	413	16.26	273	10.75
300	14	PN 25 JIS 10K JIS 20K	310	12.2	375	14.76	404	15.91	268	10.55

D	N	Pressure rating		A]	В]	D]	Н
[mm]	[inch]		[mm]	[inch]	[mm]	[inch]	[mm]	[inch]	[mm]	[inch]
		PN 6								
350	14"	PN 10	420	16.5	420	16.54	479	18.86	365	14.37
		PN 16	-							
375	15"	PN 16	461	18.2	461	18.2	523	20.6	395	15.6
		PN 6								
400	16"	PN 10	470	18.5	470	18.50	542	21.34	395	15.55
		PN 16								
		PN 6								
450	18"	PN 10	525	20.7	525	20.67	583	22.95	417	16.42
		PN 16								
		PN 6								
500	20"	PN 10	575	22.6	575	22.64	650	25.59	460	18.11
		PN 16								
		PN 6								
600	24"	PN 10	676	26.6	676	26.61	766	30.16	522	20.55
		PN 16								
		PN 6	697	27.4	_	_	786	30.94	460	18.11
500	D 011	PN10	693	27.3	-	-	813	32.01	480	18.9
700	28"	PN16	687	27.1	-	-	807	31.77	490	19.29
		Cl, D	693	27.3	-	-	832	32.76	494	19.45
750	30"	Cl, D	743	29.3	-	-	833	32.8	523	20.59
		PN 6	799	31.5	-	-	893	35.16	520	20.47
000	2.21	PN 10	795	31.3	-	-	920	36.22	540	21.26
800	32"	PN 16	789	31.1	-	-	914	35.98	550	21.65
		Cl, D	795	31.3	-	-	940	37.01	561	22.09
		PN 6	897	35.3	-	-	993	39.09	570	22.44
000	261	PN 10	893	35.2	-	-	1020	40.16	590	23.23
900	36"	PN 16	886	34.9	-	-	1014	39.92	595	23.43
		Cl, D	893	35.2	-	-	1048	41.26	615	24.21
		PN 6	999	39.3	-	-	1093	43.03	620	24.41
1000	/ ₁ O"	PN 10	995	39.2	-	-	1127	44.37	650	25.59
1000	40"	PN 16	988	38.9	-	-	1131	44.53	660	25.98
		Cl, D	995	39.2	-	-	1163	45.79	675	26.57
-	42"	PN 6	1044	41.1	-	-	1220	48.03	704	27.72
		PN 6	1203	47.4	-	-	1310	51.57	733	28.86
1200	48"	PN 10	1196	47.1	-	-	1344	52.91	760	29.92
1200	40	PN 16	1196	47.1	-	-	1385	54.53	786	30.94
		Cl, D	1188	46.8	-	-	1345	52.95	775	30.51

¹⁾ In the case of DN 25 to 250, ground disks can be used for all the flange standards/pressure ratings which can be supplied in the standard version $\frac{1}{2}$

Dimensions in US units

Compact version



Order code for "Housing", option A "Aluminum, coated"

A 1)	B 1)	С	G ²⁾	Н	I ²⁾	
[in]	[in]	[in]	[in]	[in]	[in]	
6.65	2.68	3.98	7.87	2.32	5.55	

- Depending on the cable gland used: values up to + 1.18 in For version without local display: values 1.18 in 1)
- 2)

Order code for "Housing", option A "Aluminum, coated"; Ex d or XP

A 1)	В	С	G ²⁾	Н	I
[in]	[in]	[in]	[in]	[in]	[in]
7.4	3.35	4.06	8.54	2.28	6.26

- Depending on the cable gland used: values up to + 1.18 in 1)
- 2) For version without local display: values – 1.57 in

DN 1 to 12 in (25 to 300 mm): Sensor with aluminum half-shell housing

DN	1			Or	der code	for "Des	ign"				
			Options	D, E, H, I			Opt	ion C			
		D 1)	E 1) 2) 3)	F 1) 2) 3)	M 1)	D 1)	E 1) 2) 3)	F 1) 2) 3)	M 1)	К	L
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
25	1	3.31	10.67	13.98	4.72	-	-	-	-	4)	7.87
32	-	3.31	10.67	13.98	4.72	-	-	-	-	4)	7.87
40	1 ½	3.31	10.67	13.98	4.72	-	-	-	-	4)	7.87
50	2	3.31	10.67	13.98	4.72	3.31	10.67	13.98	4.72	4)	7.87
65	-	4.29	11.65	15.94	7.09	3.31	10.67	13.98	4.72	4)	7.87
80	3	4.29	11.65	15.94	7.09	3.31	10.67	13.98	4.72	4)	7.87
100	4	4.29	11.65	15.94	7.09	4.29	11.65	15.94	7.09	4)	9.84
125	-	5.91	13.23	19.13	10.24	4.29	11.65	15.94	7.09	4)	9.84
150	6	5.91	13.23	19.13	10.24	4.29	11.65	15.94	7.09	4)	11.81
200	8	7.09	14.21	21.3	12.76	5.91	13.23	19.13	10.24	4)	13.78

DN	I			Or	der code	for "Des	ign"				
			Options	D, E, H, I			Opt				
		D 1)	$D^{(1)} \mid E^{(1)(2)(3)} \mid F^{(1)(2)(3)} \mid M^{(1)} \mid D^{(1)}$					F 1) 2) 3)	M 1)	K	L
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
250	10	8.07	15.2	23.27	15.75	5.91	13.23	19.13	10.24	4)	17.72
300	12	9.06	16.18	25.24	18.11	7.09	14.21	21.3	12.76	4)	19.69

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) With order code for "Sensor option", option CG "Sensor extended neck for insulation": values + 4.33 in
- 3) For Ex d or XP versions: values + 1.18 in

DN 1 to 12 in (25 to 300 mm): Sensor with fully welded carbon steel housing

DN	J			Or	der code	for "Desig	jn"				
			Opti	on E			Opti	on C			
		D 1)	E 1) 2)	F 1) 2)	M 1)	D 1)	E 1) 2)	F 1) 2)	M 1)	K	L
[mm]	[in]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
25	1	2.76	11.42	14.17	5.51	-	-	-	-	3)	7.87
32	-	2.76	11.42	14.17	5.51	-	-	-	-	3)	7.87
40	1 ½	2.76	11.42	14.17	5.51	-	-	-	-	3)	7.87
50	2	2.76	11.42	14.17	5.51	2.76	11.42	14.17	5.51	3)	7.87
65	-	3.23	11.89	15.12	6.5	2.76	11.42	14.17	5.51	3)	7.87
80	3	3.43	12.09	15.51	6.89	2.76	11.42	14.17	5.51	3)	7.87
100	4	3.94	12.6	16.54	7.87	3.23	11.89	15.12	6.5	3)	9.84
125	-	4.45	13.11	17.56	8.9	3.43	12.09	15.51	6.89	3)	9.84
150	6	5.28	13.94	19.21	10.59	3.94	12.6	16.54	7.87	3)	11.81
200	8	6.3	14.96	21.26	12.6	4.45	13.11	17.56	8.9	3)	13.78
250	10	7.6	16.26	23.86	15.24	5.28	13.94	19.21	10.59	3)	17.72
300	12	8.58	17.24	25.83	17.2	6.3	14.96	21.26	12.6	3)	19.69

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) With order code for "Sensor option", option CG "Sensor extended neck for insulation": values + 110 mm
- 3) Depends on the liner $\rightarrow \blacksquare 101$

DN 14 to 16 in (350 to 400 mm)

			Order code	for "Design"			
			Optio	ns E, I			
D	N	D 1)	E 1) 2)	F 1) 2)	M 1)	K	L
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
350	14	11.10	18.19	29.29	22.20	3)	21.65
375	15	12.13	19.21	31.34	24.25	3)	23.62
400	16	12.13	19.21	31.34	24.25	3)	23.62

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) For Ex d or XP versions: values + 1.18 in

DN 18 to 36 in (450 to 900 mm)

			Order code for "Design"									
			Optio	ions F, J Options G, K								
D	N	D 1)	E 2)	F	M	D	Е	F	M	K	I	L
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[iː	n]
450	18	11.42	18.7	30.12	22.83	13.11	20.39	33.5	26.22	3)	23.62 ⁴⁾	25.59 ⁵⁾
500	20	12.40	19.69	32.09	24.80	14.13	21.42	35.55	28.23		23.62	25.59
600	24	14.37	21.65	36.02	28.74	16.18	23.46	39.65	32.32		23.62	30.71
700	28	16.77	24.06	40.83	33.50	20.16	27.44	47.6	40.31		27.56	35.83
750	30	18.23	25.51	43.74	36.46	20.16	27.44	47.6	40.31		29.53	38.39
800	32	18.98	26.26	45.24	37.95	21.02	28.31	49.33	41.93		31.5	40.94
900	36	20.94	28.23	49.17	41.89	24.02	31.3	55.31	47.95		35.43	46.06

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) For Ex d or XP versions: values + 1.18 in
- 3) Depends on the liner \rightarrow $\stackrel{\triangle}{=}$ 101
- 4) Order code for "Design", option F "Fixed flange, short installed length" and option J "Fixed flange, short installed length, 0 x DN inlet/outlet runs"
- Order code for "Design", option G "Fixed flange, long installed length" and option K "Fixed flange, long installed length $0 \times DN$ inlet/outlet runs"

DN 40 to 78 in (1000 to 2000 mm)

			Order code	for "Design"					
			Options	F, G, J, K					
D	N	D 1)	E 1) 2)	F 1) 2)	M 1)	K	L		
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	1	in]	
1000	40	22.91	30.2	53.11	45.83	3)	39.37 ⁴⁾	51.18 ⁵⁾	
-	42	24.33	31.61	55.94	48.66	3)	41.34 ⁴⁾	53.74 ⁵⁾	
1200	48	27.40	34.69	62.09	54.80	3)	47.24 ⁴⁾	61.42 ⁵⁾	
-	54	31.85	39.13	70.98	63.66	3)	53.15 ⁴⁾	69.09 ⁵⁾	
1400	-	31.85	39.13	70.98	63.66	3)	55.12 ⁴⁾	71.65 ⁵⁾	
-	60	35.79	43.07	78.86	71.54	3)	59.06 ⁴⁾	76.77 ⁵⁾	
1600	-	35.79	43.07	78.86	71.54	3)	62.99 ⁴⁾	81.89 ⁵⁾	
-	66	37.80	45.08	82.87	75.55	3)	64.96 ⁴⁾	84.45 ⁵⁾	
1800	72	40.00	47.28	87.28	80.00	3)	70.87 ⁴⁾	92.13 ⁵⁾	
-	78	44.37	51.65	96.02	88.74	3)	78.74 ⁴⁾	102.36 ⁵⁾	
2000	_	44.37	51.65	96.02	88.74	3)	78.74 ⁴⁾	102.36 ⁵⁾	

- The dimensions are reference values. They may vary depending on the pressure rating, design and order option.
- 2) For Ex d or XP versions: values + 1.18 in
- 4) Order code for "Design", option F "Fixed flange, short installed length" and option J "Fixed flange, short installed length, 0 x DN inlet/outlet runs"
- 5) Order code for "Design", option G "Fixed flange, long installed length" and option K "Fixed flange, long installed length $0 \times DN$ inlet/outlet runs"

DN 84 to 120 in (2200 to 3000 mm)

			Order code	for "Design"			
			Opti	on F, J			
D	N	D 1)	E 1) 2) F 1)		M 1)	К	L
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
_	84	48.31	55.59	103.9	96.61	3)	86.61
2200	-	48.31	55.59	103.9	96.61	3)	86.61
_	90	52.44	59.72	112.17	104.88	3)	94.49
2400	-	52.44	59.72	112.17	104.88	3)	94.49
-	96	56.34	63.62	119.96	112.64	3)	96.46
_	102	59.69	66.97	126.65	119.37	3)	102.36
2600	-	56.77	64.06	120.83	113.50	3)	102.36
-	108	63.07	70.35	133.43	126.14	3)	108.27
2800	-	60.91	68.19	129.09	121.77	3)	110.24
-	114	66.46	73.74	140.2	132.87	3)	114.17
3000	-	64.84	72.13	136.97	129.65	3)	118.11
-	120	69.84	77.13	146.97	139.65	3)	120.08


¹⁾ The dimensions are reference values. They may vary depending on the pressure rating, design and order

For Ex d or XP versions: values + 1.18 in Depends on the liner $\rightarrow \blacksquare 101$

²⁾ 3)

Flange connections

Fixed flange



Ľ	N	A	В		D	E	L
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
25	1	4.25	3.12	4 × Ø0.63	0.5	1)	2)
40	1 ½	5	3.88	4 × Ø0.63	0.63		
50	2	6	4.75	4 × Ø0.75	0.69		
80	3	7.5	6	4 × Ø0.75	0.88		
100	4	9	7.5	8 × Ø0.75	0.88		
150	6	11	9.5	8 × Ø0.88	0.94		
200	8	13.5	11.75	8 × Ø0.88	1.06		
250	10	16	14.25	12 × Ø1	1.17		
300	12	19	17	12 × Ø1	1.19		
350	14	21.06	18.75	12 × Ø1.13	1.39		
400	16	23.43	21.25	16 × Ø1.13	1.46		
450	18	25	22.75	16 × Ø1.25	1.58		
500	20	27.56	25	20 × Ø1.25	1.7		
600	24	32.09	29.5	20 × Ø1.37	1.89		

- Depends on the liner $\rightarrow~$ $\stackrel{ riangle}{ riangle}$ 101
- 1) 2)

Flange according to ASME B16.5, Class 300 Carbon steel: order code for "Process connection", option A2K Stainless steel: order code for "Process connection", option A2S								
D	N	A	В	С	D	E	L	
[in]	[mm]	[in]	[in]	[in]	[in]	[in]	[in]	
1	25	4.88	3.5	4 × Ø0.75	0.63	1)	2)	
1 ½	40	6.12	4.5	4 × Ø0.88	0.75			
2	50	6.5	5	8 × Ø0.75	0.82			


Carbon steel	Flange according to ASME B16.5, Class 300 Carbon steel: order code for "Process connection", option A2K Stainless steel: order code for "Process connection", option A2S								
D	N	A	В	С	D	E	L		
[in]	[mm]	[in]	[in]	[in]	[in]	[in]	[in]		
3	80	8.25	6.62	8 × Ø0.88	1.06				
4	100	10	7.88	8 × Ø0.88	1.19				
6	150	12.5	10.62	12 × Ø0.88	1.38				
Surface rough	Surface roughness (flange): Ra 250 to 492 µm								

- 1) Depends on the liner \rightarrow $\stackrel{\triangle}{=}$ 101

	cording to A	,		1K			
D	N	A	В	С	D	E	L
[in]	[mm]	[in]	[in]	[in]	[in]	[in]	[in]
28	700	36.50	34.00	28 × Ø1.38	1.31	1)	2)
30	-	38.74	36.00	28 × Ø1.38	1.38		
32	800	41.73	38.50	28 × Ø1.65	1.50		
36	900	45.98	42.75	32 × Ø1.65	1.63		
40	1000	50.75	47.25	36 × Ø1.65	1.63		
42	-	52.99	49.50	36 × Ø1.65	1.75		
48	1200	59.49	56.00	44 × Ø1.65	1.88		
54	-	66.26	62.75	44 × Ø1.89	2.13		
60	-	73.03	69.25	52 × Ø1.89	2.25		
66	-	80.00	76.00	52 × Ø1.89	2.50		
72	1800	86.50	82.50	60 × Ø1.89	2.63		
78	-	92.99	89.00	64 × Ø2.13	2.75		
84	-	99.80	95.50	64 × Ø2.13	2.88		
90	-	106.50	107.00	68 × Ø2.36	3.00		
96	-	113.27	108.50	68 × Ø2.37	3.25		
102	-	120.00	114.50	68 × Ø2.63	3.25		
108	-	126.73	120.75	68 × Ø2.63	3.38		
114	-	133.50	126.75	68 × Ø2.87	3.50		
120	-	140.24	132.75	68 × Ø2.87	3.50		
Surface ro	ughness (fla	ange): Ra 2	50 to 492 μ	in			

- Total installed length is independent of the process connections. Installed length according to DVGW (German Technical and Scientific Association for Gas and Water) →

Lap joint flange



A0037862

Carbon ste	Lap joint flange according to ASME B16.5, Class 150 Carbon steel: order code for "Process connection", option A12 Stainless steel: order code for "Process connection", option A14									
D	N	A	В		D	E	F	L		
[mm]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]		
25	1	4.33	3.15	4 × Ø0.63	0.55	1.93	1)	2)		
40	1 ½	4.92	3.86	4 × Ø0.63	0.69	2.8				
50	2	5.91	4.76	4 × Ø0.75	0.75	3.46				
80	3	7.48	5.98	4 × Ø0.75	0.94	4.72				
100	4	9.06	7.48	8 × Ø0.75	0.94	5.83				
150	6	11.02	9.49	8 × Ø0.91	0.98	8.23				
200	8	13.58	11.73	8 × Ø0.91	1.14	10.39				
250	10	15.94	14.25	12 × Ø0.98	1.18	12.48				
300	12	19.09	17.01	12 × Ø0.98	1.26	14.88				
Surface rou	ghness (flan	ge): Ra 248 t	to 492 µin							

- 1) Depends on the liner \rightarrow $\stackrel{ riangle}{ riangle}$ 101


Accessories

External WLAN antenna



The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



■ 40 Engineering unit mm (in)

External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/reception conditions at the transmitter mounting location are poor.



■ 41 Engineering unit mm (in)

Weight

All values (weight exclusive of packaging material) refer to devices with flanges of the standard pressure rating.

The weight may be lower than indicated depending on the pressure rating and design.

Weight specifications including transmitter as per order code for "Housing", option A "Aluminum, coated".

Different values due to different transmitter versions:

Transmitter version for the hazardous area

(Order code for "Housing", option A "Aluminum, coated"; Ex d): $\pm 2 \text{ kg (} \pm 4.4 \text{ lbs)}$

Weight in SI units

Order code for "D	esign", option C, D), E, H, I : DN 25 to 400 mm (1 to 16 i	in)			
Nominal	diameter	Reference	ce values			
		EN (DIN), AS, JIS				
[mm]	[in]	Pressure rating	[kg]			
25	1	PN 40	10			
32	_	PN 40	11			
40	1 ½	PN 40	12			
50	2	PN 40	13			
65	_	PN 16	13			
80	3	PN 16	15			
100	4	PN 16	18			
125	-	PN 16	25			
150	6	PN 16	31			
200	8	PN 10	52			
250	10	PN 10	81			
300	12	PN 10	95			
350	14	PN 6	106			
375	15	PN 6	121			
400	16	PN 6	121			

Order code for "D	esign", option F, J:	DN 450 to 2000 mm (18 to 78 in)	
		Referer	nce values
Nominal	diameter	EN (DIN) (PN16)	AS (PN 16)
[mm]	[in]	[kg]	[kg]
450	18	142	138
500	20	182	186
600	24	227	266
700	28	291	369
_	30	-	447
800	32	353	524
900	36	444	704
1000	40	566	785
-	42	-	-
1200	48	843	1229
_	54	-	-
1400	_	1204	-

Order code for "D	Order code for "Design", option F, J: DN 450 to 2 000 mm (18 to 78 in)								
		Reference values							
Nominal diameter		EN (DIN) (PN16)	AS (PN 16)						
[mm]	[in]	[kg]	[kg]						
_	60	_	-						
1600	-	1845	-						
-	66	-	-						
1800	72	2357	-						
-	78	2 9 2 9	-						
2000	-	2 929	-						

Order code for "D	Order code for "Design", option F, J: DN 2 200 to 3 000 mm (84 to 120 in)					
		Reference values				
Nominal	diameter	EN (DIN) (PN6)				
[mm]	[in]	[kg]				
_	84	-				
2200	_	3 422				
_	90	-				
2400	_	4094				
_	96	-				
_	102	-				
2600	_	6433				
_	108	-				
2800	-	7 195				
-	114	-				
3000	-	8567				
-	120	-				

Order code for "Design", option G, K: DN 450 to 2000 mm (18 to 78 in)				
		Reference values		
Nominal	diameter	EN (DIN) (PN 6)		
[mm]	[in]	[kg]		
450	18	161		
500	20	156		
600	24	208		
700	28	304		
_	30	-		
800	32	357		
900	36	485		
1000	40	589		
-	42	-		
1200	48	850		
-	54	850		

Order code for "Design", option G, K: DN 450 to 2000 mm (18 to 78 in)					
		Reference values			
Nominal	diameter	EN (DIN) (PN 6)			
[mm]	[in]	[kg]			
1400	-	1300			
_	60	-			
1600	-	1845			
_	66	-			
1800	72	2 357			
_	78	2 929			
2000	-	2 929			

Weight in US units

Order code for "D	Order code for "Design", option C, D, E, H, I: DN 1 to 16 in (25 to 400 mm)					
Nominal	diameter	Reference values ASME (Class 150)				
[mm]	[in]	[16]				
25	1	11				
32	_	-				
40	1 ½	15				
50	2	20				
65	_	-				
80	3	31				
100	4	42				
125	_	-				
150	6	73				
200	8	115				
250	10	198				
300	12	284				
350	14	379				
375	15	-				
400	16	448				

Order code for "Design", option F, J: DN 18 to 120 in (450 to 3 000 mm)						
Nominal	diameter	Reference values ASME (Class 150), AWWA (Class D)				
[mm]	[in]	[lb]				
450	18	421				
500	20	503				
600	24	666				
700	28	587				
-	30	701				
800	32	845				
900	36	1036				

Order code for "D	Order code for "Design", option F, J: DN 18 to 120 in (450 to 3 000 mm)						
Nominal	diameter	Reference values ASME (Class 150), AWWA (Class D)					
[mm]	[in]	[1b]					
1000	40	1294					
_	42	1477					
1200	48	1987					
_	54	2807					
1400	_	-					
-	60	3515					
1600	_	-					
-	66	4699					
1800	72	5662					
_	78	6864					
2000	-	6864					
_	84	8280					
2200	-	-					
_	90	10577					
2400	-	-					
-	96	15 575					
-	102	18024					
2600	_	-					
_	108	20783					
2800	_	-					
-	114	24060					
3000	-	-					
-	120	27724					

Order code for "D	Order code for "Design", option G, K: DN 18 to 78 in (450 to 2000 mm)					
Nominal	diameter	Reference values ASME (Class 150), AWWA (Class D)				
[mm]	[in]	[1b]				
450	18	562				
500	20	628				
600	24	893				
700	28	882				
_	30	1014				
800	32	1213				
900	36	1764				
1000	40	1984				
_	42	2 426				
1200	48	3 087				
-	54	4851				
1400	-	-				

100

Order code for "D	Order code for "Design", option G, K: DN 18 to 78 in (450 to 2 000 mm)						
Reference values Nominal diameter ASME (Class 150), AWWA (Class D)							
[mm]	[in]	[lb]					
_	60	5 954					
1600	_	-					
_	66	8 158					
1800	72	9 040					
_	78	10143					
2000	-	-					

Measuring tube specification

The values are reference values and can vary depending on the pressure rating, design and order option.

Nominal	diameter		Pressu	Measuring tube internal diameter								
		EN (DIN)	ASME	AS 2129	JIS	Hard rubber		Polyur	ethane	РТ	FE	
			AWWA	AS 4087								
[mm]	[in]					[mm]	[in]	[mm]	[in]	[mm]	[in]	
25	1	PN 40	Class 150	-	20K	-	-	24	0.93	25	1.00	
32	-	PN 40	-	-	20K	-	-	32	1.28	34	1.34	
40	1 1/2	PN 40	Class 150	-	20K	-	-	38	1.51	40	1.57	
50	2	PN 40	Class 150	Table E, PN 16	10K	50	1.98	50	1.98	52	2.04	
50 ¹⁾	2	PN 40	Class 150	Table E, PN 16	10K	32	1.26	-	-	-	-	
65	-	PN 16	-	-	10K	66	2.60	66	2.60	68	2.67	
65 ¹⁾	-	PN 16	-	-	10K	38	1.50	-	-	-	-	
80	3	PN 16	Class 150	Table E, PN 16	10K	79	3.11	79	3.11	80	3.15	
80 ¹⁾	3	PN 16	Class 150	Table E, PN 16	10K	50	1.97	-	-	-	-	
100	4	PN 16	Class 150	Table E, PN 16	10K	101	3.99	104	4.11	104	4.09	
100 ¹⁾	4	PN 16	Class 150	Table E, PN 16	10K	66	2.60	-	-	-	-	
125	-	PN 16	-	-	10K	127	4.99	130	5.11	129	5.08	
125 ¹⁾	-	PN 16	-	-	10K	79	3.11	-	-	-	-	
150	6	PN 16	Class 150	Table E, PN 16	10K	155	6.11	158	6.23	156	6.15	
150 ¹⁾	6	PN 16	Class 150	Table E, PN 16	10K	102	4.02	-	-	-	-	
200	8	PN 10	Class 150	Table E, PN 16	10K	204	8.02	207	8.14	202	7.96	
200 1)	8	PN 16	Class 150	Table E, PN 16	10K	127	5.00	-	-	-	-	
250	10	PN 10	Class 150	Table E, PN 16	10K	258	10.14	261	10.26	256	10.09	
250 ¹⁾	10	PN 16	Class 150	Table E, PN 16	10K	156	6.14	-	-	-	-	
300	12	PN 10	Class 150	Table E, PN 16	10K	309	12.15	312	12.26	306	12.03	
300 ¹⁾	12	PN 16	Class 150	Table E, PN 16	10K	204	8.03	_	_	_	_	
350	14	PN 10	Class 150	Table E, PN 16	10K	337	13.3	340	13.4	_	_	
375	15	-	-	PN 16	10K	389	15.3	392	15.4	-	-	
400	16	PN 10	Class 150	Table E, PN 16	10K	387	15.2	390	15.4	-	-	
450	18	PN 10	Class 150	_	10K	436	17.2	439	17.3	-	-	
500	20	PN 10	Class 150	Table E, PN 16	10K	487	19.2	490	19.3	-	-	
600	24	PN 10	Class 150	Table E, PN 16	10K	585	23.0	588	23.1	-	-	

Nominal diameter			Pressu		Measuring tube internal diameter						
		EN (DIN)	ASME	AS 2129	JIS	Hard rubber		Polyur	ethane	PT	FE
			AWWA	AS 4087							
[mm]	[in]					[mm]	[in]	[mm]	[in]	[mm]	[in]
700	28	PN 10	Class D	Table E, PN 16	10K	694	27.3	697	27.4	-	-
750	30	-	Class D	Table E, PN 16	10K	743	29.3	746	29.4	_	-
800	32	PN 10	Class D	Table E, PN 16	_	794	31.3	797	31.4	-	-
900	36	PN 10	Class D	Table E, PN 16	-	895	35.2	898	35.4	-	-
1000	40	PN 6	Class D	Table E, PN 16	-	991	39.0	994	39.1	-	-
-	42	-	Class D	-	-	1043	41.1	1043	41.1	-	-
1200	48	PN 6	Class D	Table E, PN 16	-	1191	46.9	1197	47.1	-	-
-	54	-	Class D	-	_	1339	52.7	-	-	-	-
1400	-	PN 6	-	-	_	1402	55.2	-	-	-	-
-	60	-	Class D	-	_	1492	58.7	-	-	-	-
1600	-	PN 6	-	-	_	1600	63.0	-	-	-	-
-	66	-	Class D	-	_	1638	64.5	-	-	-	-
1800	72	PN 6	-	-	_	1786	70.3	-	-	-	-
-	78	-	Class D	-	_	1989	78.3	-	-	-	-
2000	-	PN 6	-	-	-	1989	78.3	-	-	-	-
-	84	-	Class D	-	_	2 099	84.0	-	-	-	-
2200	-	PN 6	-	-	_	2 194	87.8	-	-	-	-
-	90	-	Class D	-	_	2246	89.8	-	-	-	-
2400	-	PN 6	-	-	-	2391	94.1	-	-	-	-
-	96	-	Class D	-		2 382	93.8	-		-	-
-	102	-	Class D	-		2 5 3 3	99.7	-	-	-	-
2600	-	PN 6	-	-		2 580	101.6	-	-	-	-
_	108	-	Class D	-		2 683	105.6	-	-	-	-
2800	-	PN 6	-	-		2 780	109.5	-	-	-	-
_	114	-	Class D	-		2832	111.5	_	-	_	-
3000	_	PN 6	-	-		2976	117.2	_	-	-	-
_	120	-	Class D	-		2 980	117.3	_	-	_	-

1) Order code for "Design", option ${\sf C}$

Materials


Transmitter housing

Order code for "Housing": Option ${\bf A}$ "Aluminum, coated": aluminum, AlSi10Mg, coated

Window material

Order code for "Housing": Option **A** "Aluminum, coated": glass

Cable entries/cable glands



A002835

■ 42 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland $M20 \times 1.5$
- 3 Adapter for cable entry with female thread G ½" or NPT ½"
- 4 Device plug

Order code for "Housing", option A "Aluminum, coated"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material			
Compression fitting M20 × 1.5	Non-Ex: plastic			
Compression many wizo ^ 1.5	Z2, D2, Ex d/de: brass with plastic			
Adapter for cable entry with female thread G ½"	Nickel-plated brass			
Adapter for cable entry with female thread NPT ½"				

Device plug

Electrical connection	Material
Plug M12x1	 Socket: Stainless steel, 1.4404 (316L) Contact housing: Polyamide Contacts: Gold-plated brass

Sensor housing

- DN 25 to 300 (1 to 12")
 - Aluminum half-shell housing, aluminum, AlSi10Mg, coated
 - Fully welded carbon steel housing with protective varnish
- DN 350 to 3000 (14 to 120")

Fully welded carbon steel housing with protective varnish

Measuring tubes

■ DN 25 to 600 (1 to 24")

 $Stainless\ steel;\ 1.4301,\ 1.4306,\ 304,\ 304L$

DN 700 to 3000 (28 to 120")
 Stainless steel: 1.4301, 304

Liner

- DN 25 to 300 (1 to 12"): PTFE
- DN 25 to 1200 (1 to 48"): polyurethane
- DN 50 to 3000 (2 to 120"): hard rubber

Electrodes

- Stainless steel, 1.4435 (316L)
- Alloy C22, 2.4602 (UNS N06022)
- Tantalum

Process connections

- - For flanges made of carbon steel:
 - DN \leq 300 (12"): with Al/Zn protective coating or protective varnish
 - DN \geq 350 (14"): protective varnish
- All carbon steel lap joint flanges are supplied with a hot-dip galvanized finish.

EN 1092-1 (DIN 2501)

Fixed flange

- Carbon steel:
 - DN ≤ 300: S235JRG2, S235JR+N, P245GH, A105, E250C
 - DN 350 to 3000: P245GH, S235JRG2, A105, E250C
- Stainless steel:
 - DN ≤ 300: 1.4404, 1.4571, F316L
 - DN 350 to 600: 1.4571, F316L, 1.4404
 - DN 700 to 1000: 1.4404, F316L

Lap joint flange

- Carbon steel DN ≤ 300: S235JRG2, A105, E250C
- Stainless steel DN \leq 300: 1.4306,1.4404, 1.4571, F316L

Lap joint flange, stamped plate

- Carbon steel DN ≤ 300: S235JRG2 similar to S235JR+AR or 1.0038
- Stainless steel DN ≤ 300: 1.4301 similar to 304

ASME B16.5

Fixed flange, lap joint flange

- Carbon steel: A105
- Stainless steel: F316L

JIS B2220

- Carbon steel: A105, A350 LF2
- Stainless steel: F316L

AWWA C207

Carbon steel: A105, P265GH, A181 Class 70, E250C, S275JR

AS 2129

Carbon steel: A105, E250C, P235GH, P265GH, S235JRG2

AS 4087

Carbon steel: A105, P265GH, S275JR

Seals

As per DIN EN 1514-1, form IBC

Accessories

Protective cover

Stainless steel, 1.4404 (316L)

External WLAN antenna

- Antenna: ASA plastic (acrylic ester-styrene-acrylonitrile) and nickel-plated brass
- Adapter: Stainless steel and nickel-plated brass
- Cable: Polyethylene
- Plug: Nickel-plated brass
- Angle bracket: Stainless steel

Ground disks

- Stainless steel, 1.4435 (316L)
- Alloy C22, 2.4602 (UNS N06022)
- Tantalum

Fitted electrodes

Measurement, reference and empty pipe detection electrodes available as standard with:

- 1.4435 (316L)
- Alloy C22, 2.4602 (UNS N06022)
- Tantalum

Process connections

- EN 1092-1 (DIN 2501)
- ASME B16.5
- JIS B2220
- AS 2129 Table E
- AS 4087 PN 16
- AWWA C207 Class D



Surface roughness

Electrodes with 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); tantalum: < 0.5 μ m (19.7 μ in) (All data refer to parts in contact with the medium)

Operability

Operating concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnostics
- Expert level

Fast and safe commissioning

- Guided menus ("Make-it-run" wizards) for applications
- Menu quidance with brief descriptions of the individual parameter functions
- Access to the device via Web server
- WLAN access to the device via mobile handheld terminal, tablet or smart phone

Reliable operation

- Operation in local language
- Uniform operating philosophy applied to device and operating tools
- If replacing electronic modules, transfer the device configuration via the integrated memory (HistoROM backup) which contains the process and measuring device data and the event logbook. No need to reconfigure.

Efficient diagnostic behavior increases measurement availability

- Troubleshooting measures can be called up via the device and in the operating tools
- Diverse simulation options, logbook for events that occur and optional line recorder functions

Languages

Can be operated in the following languages:

- Via local operation
 English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Korean, Vietnamese, Czech, Swedish
- Via Web browser
 English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese,
 Japanese, Vietnamese, Czech, Swedish
- Via "FieldCare", "DeviceCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese

Local operation

Via display module


Equipment:

- Order code for "Display; operation", option F "4-line, illuminated, graphic display; touch control"
- Order code for "Display; operation", option G "4-line, illuminated, graphic display; touch control + W/I A N"



Information about WLAN interface →

114



A0026785

43 Operation with touch control

Display elements

- 4-line, illuminated, graphic display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F)
 The readability of the display may be impaired at temperatures outside the temperature range.


Operating elements

- External operation via touch control (3 optical keys) without opening the housing: ±, □, 国
- Operating elements also accessible in the various zones of the hazardous area

Via remote display and operating module DKX001



- The measuring device is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring device. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring device display module. Only one display or operation unit may be connected to the transmitter at any one time.



 $lap{1}{2}$ 44 Operation via remote display and operating module DKX001

A0026706

Display and operating elements

Housing material

Transmitter housing		Remote display and operating module
Order code for "Housing"	Material	Material
Option A "Aluminum, coated"	AlSi10Mg, coated	AlSi10Mg, coated

Cable entry

 $Corresponds \ to \ the \ choice \ of \ transmitter \ housing, \ order \ code \ for \ "Electrical \ connection".$

Connecting cable


→ 🖺 54

Dimensions

Remote operation


Via HART protocol

This communication interface is available in device versions with a HART output.



■ 45 Options for remote operation via HART protocol (active)

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 4 Commubox FXA 195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 Field Xpert SMT70
- 7 VIATOR Bluetooth modem with connecting cable
- 8 Transmitter




A002874

■ 46 Options for remote operation via HART protocol (passive)

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 Field Xpert SMT70
- 9 VIATOR Bluetooth modem with connecting cable
- 10 Transmitter

Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




 \blacksquare 47 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- 3 Industry network
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device

Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




 \blacksquare 48 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- *3 PROFIBUS DP network*
- 4 Measuring device

Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.




VUU38838

 \blacksquare 49 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Segment coupler PROFIBUS DP/PA
- 5 PROFIBUS PA network
- 6 T-box
- 7 Measuring device

Via Modbus RS485 protocol

This communication interface is available in device versions with a Modbus-RS485 output.



A002943


■ 50 Options for remote operation via Modbus-RS485 protocol (active)

- 1 Control system (e.g. PLC)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 3 Transmitter

Via EtherNet/IP network

This communication interface is available in device versions with EtherNet/IP.

Star topology




■ 51 Options for remote operation via EtherNet/IP network: star topology

- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 5 Measuring device

Ring topology

The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).



■ 52 Options for remote operation via EtherNet/IP network: ring topology

- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 5 Measuring device


Via PROFINET network

This communication interface is available in device versions with PROFINET.

Endress+Hauser 111

1

Star topology




■ 53 Options for remote operation via PROFINET network: star topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Ring topology


The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).



■ 54 Options for remote operation via PROFINET network: ring topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Via APL network



A0046117

 \blacksquare 55 Options for remote operation via APL network

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch, e.g. Scalance X204 (Siemens)
- 3 Computer with Web browser (e.g. Internet Explorer) for access to integrated Web server or computer with operating tool (e.g. FieldCare or DeviceCare with PROFINET COM DTM or SIMATIC PDM with FDI-Package)
- 4 APL power switch (optional)
- 5 APL field switch
- 6 Measuring device

Service interface


Via service interface (CDI-RJ45)

A point-to-point connection can be established via onsite device configuration. With the housing open, the connection is established directly via the service interface (CDI-RJ45) of the device.



An adapter for RJ45 to the M12 plug is optionally available: Order code for "Accessories", option **NB**: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can be established via an M12 plug without opening the device.




A002756

■ 56 Connection via service interface (CDI-RJ45)

- 1 Computer with Web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated Web server or with "FieldCare", "DeviceCare" operating tool with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 2 Standard Ethernet connecting cable with RJ45 plug
- 3 Service interface (CDI-RJ45) of the measuring device with access to the integrated Web server

Via WLAN interface

The optional WLAN interface is available on the following device version: Order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN"



A003457

- 1 Transmitter with integrated WLAN antenna
- 2 Transmitter with external WLAN antenna
- 3 LED lit constantly: WLAN reception is enabled on measuring device
- 4 LED flashing: WLAN connection established between operating unit and measuring device
- 5 Computer with WLAN interface and Web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device Web server or with operating tool (e.g. FieldCare, DeviceCare)
- 6 Mobile handheld terminal with WLAN interface and Web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device Web server or operating tool (e.g. FieldCare, DeviceCare)
- 7 Smart phone or tablet (e.g. Field Xpert SMT70)

Function	WLAN: IEEE 802.11 b/g (2.4 GHz) • Access Point with DHCP server (factory setting) • Network
Encryption	WPA2-PSK AES-128 (in accordance with IEEE 802.11i)
Configurable WLAN channels	1 to 11
Degree of protection	IP67
Available antennas	 Internal antenna External antenna (optional) In the event of poor transmission/reception conditions at the place of installation. Available as an accessory → ■ 122. Only 1 antenna is active at any one time!
Range	 Internal antenna: typically 10 m (32 ft) External antenna: typically 50 m (164 ft)
Materials (external antenna)	 Antenna: ASA plastic (acrylic ester-styrene-acrylonitrile) and nickel-plated brass Adapter: Stainless steel and nickel-plated brass Cable: Polyethylene Plug: Nickel-plated brass Angle bracket: Stainless steel


Network integration

Network integration is only available for the HART communication protocol.

With the optional "OPC-UA Server" application package, the device can be integrated into an Ethernet network via the service interface (CDI-RJ45 and WLAN) and communicate with OPC-UA clients. If the device is used in this way, IT security must be considered.

Transmitters with an Ex de approval may **not** be connected via the service interface (CDI-RJ45)! Order code for "Approval transmitter + sensor", options (Ex de): BB, C2, GB, MB, NB

For permanent access to device data and for device configuration via the Web server, the device is incorporated directly in a network via the service interface (CDI-RJ45). In this way, the device can be accessed any time from the control station. The measured values are processed separately via the inputs and outputs through the automation system.



A0033618


- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch
- 3 Edge Gateway
- 4 Cloud
- 5 Measuring device
- 6 Ethernet network
- 7 Measured values via inputs and outputs
- 8 Optional WLAN interface
- The optional WLAN interface is available on the following device version:
 Order code for "Display; operation", option **G** "4-line, backlit, graphic display; touch control + WLAN"

Supported operating tools

Different operating tools can be used for local or remote access to the measuring device. Depending on the operating tool used, access is possible with different operating units and via a variety of interfaces.

Supported operating tools	Operating unit	Interface	Additional information
Web browser	Notebook, PC or tablet with Web browser	 CDI-RJ45 service interface WLAN interface Ethernet-based fieldbus (EtherNet/IP, PROFINET) 	Special Documentation for the device
DeviceCare SFE100	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🖺 124
FieldCare SFE500	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🖺 124

Supported operating tools	Operating unit	Interface	Additional information
Field Xpert	SMT70/77/50	 All fieldbus protocols WLAN interface Bluetooth CDI-RJ45 service interface 	Operating Instructions BA01202S Device description files: Use update function of handheld terminal
SmartBlue app	Smart phone or tablet with iOs or Android	WLAN	→ 🗎 124



- FactoryTalk AssetCentre (FTAC) from Rockwell Automation \rightarrow www.rockwellautomation.com
- Process Device Manager (PDM) from Siemens → www.siemens.com
- Asset Management Solutions (AMS) from Emerson → www.emersonprocess.com
- FieldCommunicator 375/475 from Emerson → www.emersonprocess.com
- Field Device Manager (FDM) from Honeywell → www.process.honeywell.com
- FieldMate from Yokogawa → www.yokogawa.com
- PACTWare → www.pactware.com

The related device description files are available: www.endress.com \rightarrow Downloads

Web server


Thanks to the integrated Web server the device can be operated and configured via a Web browser and via the service interface (CDI-RJ45) or via the WLAN interface. The structure of the operating menu is the same as for the local display. In addition to the measured values, device status information is also displayed and allows users to monitor the status of the device. Furthermore the device data can be managed and the network parameters can be configured.

A device that has a WLAN interface (can be ordered as an option) is required for the WLAN connection: order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN". The device acts as an Access Point and enables communication by computer or a mobile handheld terminal.

Supported functions

Data exchange between the operating unit (such as a notebook for example) and the measuring device:

- Upload the configuration from the measuring device (XML format, configuration backup)
- Save the configuration to the measuring device (XML format, restore configuration)
- Export event list (.csv file)
- Export parameter settings (.csv file or PDF file, document the measuring point configuration)
- Export the Heartbeat verification log (PDF file, only available with the "Heartbeat Verification" application package)
- Flash firmware version for device firmware upgrade, for instance
- Download driver for system integration
- Visualize up to 1000 saved measured values (only available with the **Extended HistoROM** application package $\rightarrow \blacksquare$ 121)



HistoROM data management

The measuring device features HistoROM data management. HistoROM data management comprises both the storage and import/export of key device and process data, making operation and servicing far more reliable, secure and efficient.

When the device is delivered, the factory settings of the configuration data are stored as a backup in the device memory. This memory can be overwritten with an updated data record, for example after commissioning.

Additional information on the data storage concept

There are different types of data storage units in which device data are stored and used by the device:

	HistoROM backup	T-DAT	S-DAT
Available data	 Event logbook such as diagnostic events for example Parameter data record backup Device firmware package Driver for system integration for exporting via Web server, e.g: GSD for PROFIBUS DP GSD for PROFIBUS PA GSDML for PROFINET EDS for EtherNet/IP DD for FOUNDATION Fieldbus 	 Measured value logging ("Extended HistoROM" order option) Current parameter data record (used by firmware at run time) Maximum indicators (min/max values) Totalizer values 	 Sensor data: nominal diameter etc. Serial number Calibration data Device configuration (e.g. SW options, fixed I/O or multi I/O)
Storage location	Fixed on the user interface board in the connection compartment	Attachable to the user interface board in the connection compartment	In the sensor plug in the transmitter neck part

Data backup

Automatic

- The most important device data (sensor and transmitter) are automatically saved in the DAT modules
- If the transmitter or measuring device is replaced: once the T-DAT containing the previous device data has been exchanged, the new measuring device is ready for operation again immediately without any errors
- If the sensor is replaced: once the sensor has been replaced, new sensor data are transferred from the S-DAT in the measuring device and the measuring device is ready for operation again immediately without any errors
- If exchanging the electronics module (e.g. I/O electronics module): Once the electronics module has been replaced, the software of the module is compared against the current device firmware. The module software is upgraded or downgraded where necessary. The electronics module is available for use immediately afterwards and no compatibility problems occur.

Manual

Additional parameter data record (complete parameter settings) in the integrated device memory HistoROM backup for:

- Data backup function
 Backup and subsequent restoration of a device configuration in the device memory HistoROM backup
- Data comparison function
 Comparison of the current device configuration with the device configuration saved in the device memory HistoROM backup

Data transmission

Manual

- Transfer of a device configuration to another device using the export function of the specific operating tool, e.g. with FieldCare, DeviceCare or Web server: to duplicate the configuration or to store in an archive (e.g. for backup purposes)
- Transmission of the drivers for system integration via Web server, e.g.:
 - GSD for PROFIBUS DP
 - GSD for PROFIBUS PA
 - GSDML for PROFINET
 - EDS for EtherNet/IP
 - DD for FOUNDATION Fieldbus

Event list

Automatic

- Chronological display of up to 20 event messages in the events list
- If the Extended HistoROM application package (order option) is enabled: up to 100 event messages are displayed in the events list along with a time stamp, plain text description and remedial measures
- The events list can be exported and displayed via a variety of interfaces and operating tools e.g. DeviceCare. FieldCare or Web server

Data logging

Manual

If the **Extended HistoROM** application package (order option) is enabled:

- Record up to 1000 measured values via 1 to 4 channels
- User configurable recording interval
- Record up to 250 measured values via each of the 4 memory channels
- Export the measured value log via a variety of interfaces and operating tools e.g. FieldCare, DeviceCare or web server

Certificates and approvals

Current certificates and approvals that are available for the product can be selected via the Product Configurator at www.endress.com:

- 1. Select the product using the filters and search field.
- 2. Open the product page.
- 3. Select **Configuration**.

CE mark

The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.

Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

UKCA marking

The device meets the legal requirements of the applicable UK regulations (Statutory Instruments). These are listed in the UKCA Declaration of Conformity along with the designated standards. By selecting the order option for UKCA marking, Endress+Hauser confirms a successful evaluation and testing of the device by affixing the UKCA mark.

Contact address Endress+Hauser UK:

Endress+Hauser Ltd.

Floats Road

Manchester M23 9NF

United Kingdom


www.uk.endress.com

RCM mark

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



ATEX, IECEx

Currently, the following versions for use in hazardous areas are available:

Ex db eb

Category	Type of protection
II2G	Ex db eb ia IIC T6T1 Gb

118

Ex tb

Category	Type of protection
II2D	Ex tb IIIC Txxx Db

Ех ес

Category	Type of protection
II3G	Ex ec ic IIC T5T1 Gc

cCSAus

Currently, the following versions for use in hazardous areas are available:

IS (Ex i) and XP (Ex d)

Class I, II, III Division 1 Groups A-G

NI (Ex nA)

Class I Division 2 Groups A - D

Ex de

Class I, Zone 1 AEx/ Ex de ia IIC T6...T1 Gb

Ex nA

Class I, Zone 2 AEx/Ex nA ic IIC T5...T1 Gc

Ex tb

Zone 21 AEx/ Ex tb IIIC T** °C Db

Drinking water approval

- ACS
- KTW/W270
- NSF 61
- WRAS BS 6920

HART certification

HART interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability)

FOUNDATION Fieldbus certification

FOUNDATION Fieldbus interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified in accordance with FOUNDATION Fieldbus H1
- Interoperability Test Kit (ITK), revision version 6.2.0 (certificate available on request)
- Physical Layer Conformance Test
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFIBUS

PROFIBUS interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V./ PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

EtherNet/IP certification

The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications:

- $\, \blacksquare \,$ Certified in accordance with the ODVA Conformance Test
- EtherNet/IP Performance Test
- EtherNet/IP PlugFest compliance
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFINET

PROFINET interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V. / PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
 - Test specification for PROFINET devices
 - PROFINET Security Level 2 Netload Class 2 0 Mbps
- The device can also be operated with certified devices of other manufacturers (interoperability)
- The device supports PROFINET S2 system redundancy.

Certification PROFINET with Ethernet-APL

PROFINET interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V. \prime PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
 - Test specification for PROFINET devices
 - PROFINET PA Profile 4
 - PROFINET Security Level 2 Netload Class 2 0 Mbps
 - APL conformance test
- The device can also be operated with certified devices of other manufacturers (interoperability)
- The device supports PROFINET S2 system redundancy.

Radio approval

The measuring device has radio approval.



For detailed information on the radio approval, see the Special Documentation

Other standards and quidelines

■ EN 60529

Degrees of protection provided by enclosures (IP code)

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements

■ IEC/EN 61326-2-3

Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).

■ NAMUR NE 21

Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment

■ NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors $\,$

■ NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

■ NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices $% \left(1\right) =\left(1\right) \left(1\right) \left$

■ NAMUR NE 107

Self-monitoring and diagnosis of field devices

■ NAMUR NE 131

Requirements for field devices for standard applications

■ ETSI EN 300 328

Guidelines for 2.4 GHz radio components.

■ EN 301489

Electromagnetic compatibility and radio spectrum matters (ERM).

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

1. Select the product using the filters and search field.

- 2. Open the product page.
- 3. Select **Configuration**.

Product Configurator - the tool for individual product configuration • Up-to-the-minute configuration data

- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Diagnostic functionality

Order code for "Application package", option EA "Extended HistoROM"

Comprises extended functions concerning the event log and the activation of the measured value memory.

Event log:

Memory volume is extended from 20 message entries (standard version) to up to 100 entries.

Data logging (line recorder):

- Memory capacity for up to 1000 measured values is activated.
- 250 measured values can be output via each of the 4 memory channels. The recording interval can
 be defined and configured by the user.
- Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server.



For detailed information, see the Operating Instructions for the device.

Heartbeat Technology

Order code for "Application package", option EB "Heartbeat Verification + Monitoring"

Heartbeat Verification

Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment".

- $\ \ \blacksquare$ Functional testing in the installed state without interrupting the process.
- Traceable verification results on request, including a report.
- Simple testing process via local operation or other operating interfaces.
- Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.
- Extension of calibration intervals according to operator's risk assessment.

Heartbeat Monitoring

Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to:

- Draw conclusions using these data and other information about the impact the process influences (e.g. formation of buildup, magnetic field interference etc.) have on measuring performance over time.
- Schedule servicing in time.
- Monitor the process or product quality.



For detailed information, see the Special Documentation for the device.

Cleaning

Order code for "Application package", option EC "ECC electrode cleaning"

The electrode cleaning circuit (ECC) function has been developed to have a solution for applications where magnetite (Fe_3O_4) deposits frequently occur (e.g. hot water). Since magnetite is highly

conductive this build up leads to measuring errors and ultimately to the loss of signal. The application package is designed to avoid build-up of very conductive matter and thin layers (typical of magnetite).



For detailed information, see the Operating Instructions for the device.

OPC-UA Server

Order code for "Application package", option EL "OPC-UA Server"

The application package provides an integrated OPC-UA server for comprehensive device services for IoT and SCADA applications.



For detailed information, see the Special Documentation for the device.

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the transmitter

Accessories	Description
Proline 300 transmitter	Transmitter for replacement or storage. Use the order code to define the following specifications: Approvals Output Input Display/operation Housing Software Order code: 5X3BXX Installation Instructions EA01199D
Remote display and operating module DKX001	 If ordered directly with the measuring device: Order code for "Display; operation", option O "Remote display 4-line, illuminated; 10 m (30 ft) cable; touch control" If ordered separately: Measuring device: order code for "Display; operation", option M "W/o, prepared for remote display" DKX001: Via the separate product structure DKX001 If ordered subsequently: DKX001: Via the separate product structure DKX001
	Mounting bracket for DKX001 ■ If ordered directly: order code for "Accessory enclosed", option RA "Mounting bracket, pipe 1/2" ■ If ordered subsequently: order number: 71340960 Connecting cable (replacement cable) Via the separate product structure: DKX002 ■ Further information on display and operating module DKX001→ ■ 107. Special Documentation SD01763D

External WLAN antenna	External WLAN antenna with 1.5 m (59.1 in) connecting cable and two angle brackets. Order code for "Accessory enclosed", option P8 "Wireless antenna wide area".
	 The external WLAN antenna is not suitable for use in hygienic applications. Additional information regarding the WLAN interface → □ 114.
	Order number: 71351317
	Installation Instructions EA01238D
Weather protection cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight. ① Order number: 71343505
	Installation Instructions EA01160D
Ground cable	Set, consisting of two ground cables for potential equalization.

For the sensor

Accessories	Description
Ground disks	Are used to ground the medium in lined measuring tubes to ensure proper measurement.
	For details, see Installation Instructions EA00070D

Communication-specific accessories

Accessories	Description
Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. Technical Information TI00404F
HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. Technical Information TI00429F Operating Instructions BA00371F
Fieldgate FXA42	Is used to transmit the measured values of connected 4 to 20 mA analog measuring devices, as well as digital measuring devices Technical Information TI01297S Operating Instructions BA01778S Product page: www.endress.com/fxa42
Field Xpert SMT50	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle. Technical Information TI01342S Operating Instructions BA01709S Product page: www.endress.com/smt50

Field Xpert SMT70	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.
	 Technical Information TI01342S Operating Instructions BA01709S Product page: www.endress.com/smt70
Field Xpert SMT77	The Field Xpert SMT77 tablet PC for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1.
	 Technical Information TI01418S Operating Instructions BA01923S Product page: www.endress.com/smt77

Service-specific accessories

Accessory	Description
Applicator	Software for selecting and sizing Endress+Hauser measuring devices: Choice of measuring devices with industrial requirements Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy. Graphic illustration of the calculation results Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.
	Applicator is available: • Via the Internet: https://portal.endress.com/webapp/applicator • As a downloadable DVD for local PC installation.
W@M	W@M Life Cycle Management Improved productivity with information at your fingertips. Data relevant to a plant and its components is generated from the first stages of planning and during the asset's complete life cycle. W@M Life Cycle Management is an open and flexible information platform with online and on-site tools. Instant access for your staff to current, in-depth data shortens your plant's engineering time, speeds up procurement processes and increases plant uptime. Combined with the right services, W@M Life Cycle Management boosts productivity in every phase. For more information, see: www.endress.com/lifecyclemanagement
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition. Operating Instructions BA00027S and BA00059S
DeviceCare	Tool for connecting and configuring Endress+Hauser field devices. Innovation brochure IN01047S

System components

Accessories	Description
Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.
	 Technical Information TI00133R Operating Instructions BA00247R
iTEMP	The temperature transmitters can be used in all applications and are suitable for the measurement of gases, steam and liquids. They can be used to read in the medium temperature.
	"Fields of Activity" document FA00006T

Supplementary documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- Device Viewer (www.endress.com/deviceviewer): Enter serial number from nameplate.
- Endress+Hauser Operations app: Enter serial number from nameplate or scan matrix code on nameplate.

Standard documentation

Brief Operating Instructions

Brief Operating Instructions for the sensor

Measuring device	Documentation code
Proline Promag W	KA01266D

Brief Operating Instructions for the transmitter

	Documentation code							
Measuring device	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Proline 300	KA01308D	KA01294D	KA01405D	KA01385D	KA01310D	KA01338D	KA01340D	KA01516D

Operating Instructions

Measuring device	Documentation code							
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Promag W 300	BA01918D	BA01938D	BA01928D	BA01940D	BA01939D	BA01937D	BA01941D	BA02104D

Description of Device Parameters

Measuring device	Documentation code							
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Promag 300	GP01051D	GP01098D	GP01052D	GP01135D	GP01053D	GP01113D	GP01112D	GP01172D

Supplementary devicedependent documentation

Safety instructions

Safety instructions for electrical equipment for hazardous areas.

Contents	Documentation code
ATEX/IECEx Ex d/Ex de	XA01414D
ATEX/IECEx Ex ec	XA01514D
cCSAus XP	XA01515D
cCSAus Ex d/ Ex de	XA01516D
cCSAus Ex nA	XA01517D
INMETRO Ex d/Ex de	XA01518D
INMETRO Ex ec	XA01519D
NEPSI Ex d/Ex de	XA01520D

Contents	Documentation code
NEPSI Ex nA	XA01521D
EAC Ex d/Ex de	XA01656D
EAC Ex nA	XA01657D
JPN Ex d	XA01775D

Remote display and operating module DKX001

Contents	Documentation code
ATEX/IECEx Ex i	XA01494D
ATEX/IECEx Ex ec	XA01498D
cCSAus IS	XA01499D
cCSAus Ex nA	XA01513D
INMETRO Ex i	XA01500D
INMETRO Ex ec	XA01501D
NEPSI Ex i	XA01502D
NEPSI Ex nA	XA01503D

Functional Safety Manual

Contents	Documentation code
Promag 300	SD01740D

Special Documentation

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01614D
Radio approvals for WLAN interface for A309/A310 display module	SD01793D
Remote display and operating module DKX001	SD01763D
OPC-UA server 1)	SD02043D

1) This Special Documentation is only available for device versions with a HART output.

Contents	Documentation code							
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	PROFINET	EtherNet/IP	PROFINET with Ethernet- APL
Heartbeat Technology	SD01640D	SD01742D	SD01744D	SD02206D	SD01743D	SD01986D	SD01980D	SD02729D
Web server	SD01654D	SD01657D	SD01656D	SD02235D	SD01655D	SD01977D	SD01976D	SD02768D

Installation Instructions

Contents	Comment
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory \rightarrow $\ \ \ \ $ $\ \ $ $\ \ $ $\ \ $ $\ \ $ $\ \ $ $\ \ $ $\ \ $ $\ \ $ $\ \ $ $\ \ $

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

PROFIBUS[®]

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

FOUNDATION™ Fieldbus

Registration-pending trademark of the FieldComm Group, Austin, Texas, USA

Modbus

Registered trademark of SCHNEIDER AUTOMATION, INC.

EtherNet/IP™

Trademark of ODVA, Inc.

$\textbf{Ethernet-APL}^{\intercal M}$

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

PROFINET®

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany



www.addresses.endress.com

