

# Safety Instructions

## Micropilot

### FMR50/51/52/53/54/56/57

PROFIBUS PA, FOUNDATION Fieldbus

ATEX, IECEx: Ex ia IIC T6 Ga  
Ex ia IIC T6 Ga/Gb



---

# Micropilot FMR50/51/52/53/54/56/57

PROFIBUS PA, FOUNDATION Fieldbus

## Table of contents

Associated documentation ..... 4

Supplementary documentation ..... 4

Certificates and declarations ..... 4

Manufacturer address ..... 5

Other standards ..... 5

Extended order code ..... 5

Safety instructions: General ..... 10

Safety instructions: Specific conditions of use ..... 11

Safety instructions: Installation ..... 13

Safety instructions: Zone 0 ..... 16

Temperature tables ..... 16

Connection data ..... 18

**Associated documentation**

All documentation is available on the Internet:

[www.endress.com/Deviceviewer](http://www.endress.com/Deviceviewer)

(enter the serial number from the nameplate).



If not yet available, a translation into EU languages can be ordered.

To commission the device, please observe the Operating Instructions pertaining to the device:

PROFIBUS PA

- BA01124F (FMR50)
- BA01125F (FMR51, FMR52)
- BA01126F (FMR53, FMR54)
- BA01127F (FMR56, FMR57)

FOUNDATION Fieldbus

- BA01120F (FMR50)
- BA01121F (FMR51, FMR52)
- BA01122F (FMR53, FMR54)
- BA01123F (FMR56, FMR57)

**Supplementary documentation**

Explosion protection brochure: CP00021Z

The explosion protection brochure is available on the Internet:

[www.endress.com/Downloads](http://www.endress.com/Downloads)

**Certificates and declarations****EU Declaration of Conformity**

Declaration Number:

EU\_00954

The EU Declaration of Conformity is available on the Internet:

[www.endress.com/Downloads](http://www.endress.com/Downloads)

**EU type-examination certificate**

Certificate number:

PTB 12 ATEX 2018 X

List of applied standards: See EU Declaration of Conformity.

**IEC Declaration of Conformity**

Certificate number:

IECEX PTB 12.0044 X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

- IEC 60079-0 : 2017
- IEC 60079-11 : 2011
- IEC 60079-26 : 2021

Manufacturer  
address

Endress+Hauser SE+Co. KG  
Hauptstraße 1  
79689 Maulburg, Germany  
Address of the manufacturing plant: See nameplate.

## Other standards

Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres - Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres - Explosion prevention and protection - Part 1: Basic concepts and methodology"

Extended  
order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

### Structure of the extended order code

|                  |   |                           |   |                              |
|------------------|---|---------------------------|---|------------------------------|
| FMR5x            | - | *****                     | + | A*B*C*D*E*F*G*..             |
| (Device<br>type) |   | (Basic<br>specifications) |   | (Optional<br>specifications) |

\* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

### Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

### Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group

and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

**Extended order code: Micropilot**

-  The following specifications reproduce an extract from the product structure and are used to assign:
- This documentation to the device (using the extended order code on the nameplate).
  - The device options cited in the document.

*Device type*  
FMR50, FMR51, FMR52, FMR53, FMR54, FMR56, FMR57

*Basic specifications*

| Position 1, 2 (Approval) |    |                                       |
|--------------------------|----|---------------------------------------|
| Selected option          |    | Description                           |
| FMR5x                    | BA | ATEX II 1 G Ex ia IIC T6...T1 Ga      |
|                          | BB | ATEX II 1/2 G Ex ia IIC T6...T1 Ga/Gb |
|                          | IA | IECEX Ex ia IIC T6...T1 Ga            |
|                          | IB | IECEX Ex ia IIC T6...T1 Ga/Gb         |


| Position 3 (Power Supply, Output) |   |                                                  |
|-----------------------------------|---|--------------------------------------------------|
| Selected option                   |   | Description                                      |
| FMR5x                             | E | 2-wire, FOUNDATION Fieldbus, switch output (PFS) |
|                                   | G | 2-wire, PROFIBUS PA, switch output (PFS)         |

| Position 4 (Display, Operation) |                    |                                                            |
|---------------------------------|--------------------|------------------------------------------------------------|
| Selected option                 |                    | Description                                                |
| FMR5x                           | A                  | Without, via communication                                 |
|                                 | C                  | SD02, 4-line, push buttons + data backup function          |
|                                 | E                  | SD03, 4-line, illum., touch control + data backup function |
|                                 | L <sup>1) 2)</sup> | Prepared for display FHX50 + M12 connection                |
|                                 | M <sup>1) 2)</sup> | Prepared for display FHX50 + custom connection             |
|                                 | N <sup>1) 3)</sup> | Prepared for display FHX50 + NPT1/2"                       |


- 1) FHX50 is approved according to DEK12.0046X or DEKRA 12ATEX0151X.
- 2) In connection with Position 5 = A: Observe the specifications in the "Overvoltage protection" and "Temperature tables" chapters!
- 3) Only in connection with Position 5 = B, C


| Position 5 (Housing) |   |                                     |
|----------------------|---|-------------------------------------|
| Selected option      |   | Description                         |
| FMR5x                | A | GT19 dual compartment, plastics PBT |
|                      | C | GT20 dual compartment, Alu coated   |
| FMR51-54<br>FMR57    | B | GT18 dual compartment, 316L         |

| Position 7, 8 (Antenna) |                  |                                                                                     |
|-------------------------|------------------|-------------------------------------------------------------------------------------|
| Selected option         |                  | Description                                                                         |
| FMR50                   | BM <sup>1)</sup> | Horn 40 mm/1½", PVDF encapsulated, -40...130°C                                      |
|                         | BN               | Horn 80 mm/3", PP cladde, -40...80°C                                                |
|                         | BR               | Horn 100 mm/4", PP cladde, -40...80°C                                               |
| FMR51                   | Bx               | Horn (different sizes)                                                              |
| FMR52                   | BO               | Horn 50 mm/2", -40...200°C <sup>2)</sup> , -196...200°C <sup>3)</sup> , flush mount |
|                         | BP               | Horn 80 mm/3", -40...200°C <sup>2)</sup> , -196...200°C <sup>3)</sup> , flush mount |
| FMR53                   | Cx               | Rod (different sizes)                                                               |
| FMR54                   | Ax               | Without Horn                                                                        |
|                         | Bx               | Horn (different sizes)                                                              |
|                         | Dx               | Planar (different sizes)                                                            |
| FMR56                   | BN               | Horn 80 mm/3", PP cladde, -40...80°C                                                |
|                         | BR               | Horn 100 mm/4", PP cladde, -40...80°C                                               |

| Position 7, 8 (Antenna)                                                                                                                                                                                                                                   |    |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|-----------------------------|
| Selected option                                                                                                                                                                                                                                           |    | Description                 |
| FMR57                                                                                                                                                                                                                                                     | Bx | Horn (different sizes)      |
|                                                                                                                                                                                                                                                           | Fx | Parabolic (different sizes) |
| <div><div> Shown in the temperature tables exemplary as follows:</div><div></div></div> |    |                             |

- 1) Only in connection with Position 1, 2 = BA, IA
- 2) In connection with Position 5 = A
- 3) Only in connection with Position 5 = B, C

| Position 9, 10 (Seal)                                                                                                                                                                                                                                         |    |                                                  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|--------------------------------------------------|
| Selected option                                                                                                                                                                                                                                               |    | Description                                      |
| FMR51                                                                                                                                                                                                                                                         | A5 | Viton GLT, -40...150°C                           |
|                                                                                                                                                                                                                                                               | C1 | Kalrez, -20...150°C                              |
|                                                                                                                                                                                                                                                               | D2 | Graphite, -196...450°C (HT)                      |
|                                                                                                                                                                                                                                                               | D3 | Graphite, -40...250°C (XT)                       |
| FMR54                                                                                                                                                                                                                                                         | A7 | Viton, -20...150°C (Planar)                      |
|                                                                                                                                                                                                                                                               | A8 | Viton, -40...200°C                               |
|                                                                                                                                                                                                                                                               | B4 | EPDM, -40...150°C                                |
|                                                                                                                                                                                                                                                               | C2 | Kalrez, -20...200°C, conductive media max. 150°C |
|                                                                                                                                                                                                                                                               | D1 | Graphite, -196...280°C (XT)                      |
|                                                                                                                                                                                                                                                               | D2 | Graphite, -196...400°C (HT)                      |
| FMR57                                                                                                                                                                                                                                                         | A6 | Viton GLT, -40...200°C                           |
|                                                                                                                                                                                                                                                               | D4 | Graphite, -40...400°C (HT)                       |
| <div><div> Shown in the temperature tables exemplary as follows:</div><div></div></div> |    |                                                  |

| Position 11-13 (Process Connection)                                                                                                                                                                                                                                           |                   |                                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|---------------------------------------------|
| Selected option                                                                                                                                                                                                                                                               |                   | Description                                 |
| FMR51-54                                                                                                                                                                                                                                                                      | Axx<br>Cxx<br>Kxx | Flange (different sizes)                    |
| FMR50                                                                                                                                                                                                                                                                         | GGF<br>RGF        | Thread, PVDF                                |
|                                                                                                                                                                                                                                                                               | UAE               | Mounting bracket                            |
|                                                                                                                                                                                                                                                                               | XR0               | Connection, without flange/mounting bracket |
|                                                                                                                                                                                                                                                                               | XxG               | Slip on flange (different sizes)            |
| FMR51                                                                                                                                                                                                                                                                         | Pxx               | Flange (different sizes)                    |
|                                                                                                                                                                                                                                                                               | Rxx               | Thread                                      |
|                                                                                                                                                                                                                                                                               | Txx               | Tri-Clamp                                   |
| FMR52                                                                                                                                                                                                                                                                         | Mxx               | Slotted-nut                                 |
|                                                                                                                                                                                                                                                                               | Txx               | Tri-Clamp                                   |
| FMR53                                                                                                                                                                                                                                                                         | RxJ               | Thread, 316L                                |
|                                                                                                                                                                                                                                                                               | RxF               | Thread, PVDF                                |
| FMR56                                                                                                                                                                                                                                                                         | UAE               | Mounting bracket                            |
|                                                                                                                                                                                                                                                                               | XR0               | Connection, without flange/mounting bracket |
|                                                                                                                                                                                                                                                                               | XxG               | Slip on flange (different sizes)            |
| FMR57                                                                                                                                                                                                                                                                         | RxJ               | Thread, 316L                                |
|                                                                                                                                                                                                                                                                               | XxJ               | Align. device (different sizes)             |
| <div><div></div><div>Shown in the temperature tables<br/>exemplary as follows:</div></div> <div></div> |                   |                                             |

| Position 14 (Air Purge Connection) |   |             |
|------------------------------------|---|-------------|
| Selected option                    |   | Description |
| FMR57                              | 1 | G1/4        |
|                                    | 2 | NPT1/4      |

Optional specifications

| ID Jx (Test, Certificate)                           |                  |                                       |
|-----------------------------------------------------|------------------|---------------------------------------|
| Selected option                                     |                  | Description                           |
| FMR51 <sup>1)</sup><br>FMR52<br>FMR54 <sup>2)</sup> | JN <sup>3)</sup> | Ambient temperature transmitter -50°C |

- 1) Only in connection with Position 9, 10 = D2
- 2) Only in connection with Position 9, 10 = D1, D2
- 3) Only in connection with Position 5 = B, C

| ID Nx, Ox (Accessory Mounted) |                |                                             |
|-------------------------------|----------------|---------------------------------------------|
| Selected option               |                | Description                                 |
| FMR5x                         | NA             | Overvoltage protection                      |
| FMR51                         | OM<br>OU<br>OV | Antenna extension (different sizes)         |
|                               | OW             | Horn protection, PTFE, no airpurge possible |
| FMR54                         | OM             | Antenna extension (different sizes)         |
|                               | ON             |                                             |
|                               | OR             |                                             |
|                               | OS             |                                             |
| FMR57                         | OP<br>OT       | Antenna extension (different sizes)         |
|                               | OW             | Horn protection, PTFE, no airpurge possible |

Safety instructions:  
General

- The device is intended to be used in explosive atmospheres as defined in the scope of IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications.
- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
  - Be suitably qualified for their role and the tasks they perform
  - Be trained in explosion protection
  - Be familiar with national regulations
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.

- Avoid electrostatic charging:
  - Of plastic surfaces (e.g. enclosure, sensor element, special varnishing, attached additional plates, ...)
  - Of isolated capacities (e.g. isolated metallic plates)
- Alterations to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application and the temperature class.

**Safety  
instructions:  
Specific  
conditions of use**

Permitted ambient temperature range at the electronics enclosure:  
 $-40\text{ °C} \leq T_a \leq +80\text{ °C}$

*Optional specification, ID Jx = JN*

Permitted ambient temperature range at the electronics enclosure:  
 $-50\text{ °C} \leq T_a \leq +80\text{ °C}$

- Observe the information in the temperature tables.
- In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic surfaces.
- To avoid electrostatic charging: Do not rub surfaces with a dry cloth.
- In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:
  - Observe the danger of electrostatic charging and discharge.
  - Do not install in the vicinity of processes ( $\leq 0.5\text{ m}$ ) generating strong electrostatic charges.


*Basic specification, Position 1, 2 = BB, IB*

- The probe must not be subjected to abrasive or corrosive medium that may adversely affect the partition for the zone separation.
- The zone partition wall of the device is a gas-tight feed through made of stainless-steel adapter and glass conductor bushing.

| Sensor                     | Zone partition wall material | Wall thickness | Diameter |
|----------------------------|------------------------------|----------------|----------|
| FMR50-52<br>FMR56<br>FMR57 | Stainless-steel adapter      | 6 mm           | 10 mm    |
|                            | Glass conductor bushing      | 2.6 mm         | 2.4 mm   |
|                            | Welding seam                 | > 0.2 mm       | -        |
| FMR53<br>FMR54             | Stainless-steel adapter      | 14 mm          | 25 mm    |
|                            | Glass conductor bushing      | 4.8 mm         | 6.3 mm   |
|                            | Welding seam                 | > 0.2 mm       | -        |

### Basic specification, Position 5 = A

Avoid electrostatic charging of the enclosure (e.g. friction, cleaning, maintenance, strong medium flow).



A0032146

- 1 Isolated capacitance:  
with one metal plate:  $\leq 3 \text{ pF}$  (permitted in all areas for Equipment Groups II and III)  
with two to three metal plates:  $\leq 10 \text{ pF}$  (not permitted in Zone 0 and for Equipment Group IIC)
- 2 Enclosure

### Basic specification, Position 5 = C

In Zone 0, avoid sparks caused by impact and friction.

*Device type FMR50, FMR52, FMR53, FMR54 (planar, enamel), FMR56*  
An antenna coated with non-conductive material can be used if avoiding electrostatic charging (e.g. through friction, cleaning, maintenance, strong medium flow).

*Device type FMR51, FMR57 and Optional specification, ID Nx, Ox = OW*  
An antenna coated with non-conductive material can be used if avoiding electrostatic charging (e.g. through friction, cleaning, maintenance, strong medium flow).

### Device type FMR57 and Basic specification, Position 11-13 = XxJ

- Changing the position of the alignment device must be impossible:
  - After the alignment of the antenna via the pivot bracket
  - After tightening of the clamping flange
  - After setting the damping ring (torque 15 Nm)
- Degree of protection IP67 must be fulfilled.


### Device type FMR57 and Basic specification, Position 14 = 1, 2

- If equipment with Ga/Gb or Da/Db is required: In the closed state the minimum degree of protection of the installation must be IP67.
- After removing the air purge connection: Lock the opening with a suitable plug.
  - Torque: 6-7 Nm
  - For Da/Db: thread engagement > 5 turns
- Degree of protection IP67 must be fulfilled.

Device type FMR51, FMR54, FMR57 and Optional specification, ID Nx,  
Ox = OM, ON, OR, OS, OU, OV, OP, OT

Avoid contact between sensor and tank wall. Take into account tank fittings and flow conditions (avoid sparks caused by impact and friction).

## Safety instructions: Installation



A0025536

- A Zone 0, Zone 1
- 1 Tank; Zone 0, Zone 1
- 2 Electronic insert
- 3 Enclosure
- 4 Certified associated apparatus
- 5 Potential equalization line
- 6 Potential equalization

- After aligning (rotating) the enclosure, retighten the fixing screw (see Operating Instructions).
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.
- Continuous service temperature of the connecting cable:  
-40 °C to  $\geq +85$  °C; in accordance with the range of service temperature taking into account additional influences of the process conditions ( $T_{a,min}$ ), ( $T_{a,max} + 20$  K).

Optional specification, ID Jx = JN

Continuous service temperature of the connecting cable:  
-50 °C to  $\geq +85$  °C; in accordance with the range of service temperature taking into account additional influences of the process conditions ( $T_{a,min}$ ), ( $T_{a,max} + 20$  K).

*Basic specification, Position 4 = N*


Observe the requirements according to IEC/EN 60079-14 for conduit systems and the wiring and installation instructions of the suitable Safety Instructions (XA). In addition, observe national regulations and standards for conduit systems.

**Intrinsic safety**

- The device is only suitable for connection to certified, intrinsically safe equipment with explosion protection Ex ia / Ex ib.
- The intrinsically safe input power circuit of the device is isolated from ground. If the device is only equipped with one input, the dielectric strength of the input is at least  $500 V_{\text{rms}}$ . If the device is equipped with more than one input, the dielectric strength of each individual input to ground is at least  $500 V_{\text{rms}}$ , and the dielectric strength of the inputs vis-à-vis one another is also at least  $500 V_{\text{rms}}$ .
- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- The device can be connected to the Endress+Hauser FXA291 service tool: refer to the Operating Instructions and specifications in the "Overvoltage protection" chapter.
- When the intrinsically safe Ex ia circuits of the device are connected to certified intrinsically safe circuits of Category Ex ib for Equipment Groups IIC or IIB, the type of protection changes to Ex ib [ia] IIC or Ex ib [ia] IIB. Regardless of the power supply, all the internal circuits correspond to Ex ia IIC type of protection (e.g. service interface, external display, sensor).

**Potential equalization**

- Integrate the device into the local potential equalization.
- Grounding the screen, see the following figure.



A0022352

- A Version 1: Use small capacitors (e.g. 1 nF, 1500 V dielectric strength, ceramic). Total capacitance connected to the screen may not exceed 10 nF.
- B Version 2
- 1 Terminating resistor
- 2 Distributor/T box
- 3 Screen insulated
- 4 Supply unit/Segment coupler
- 5 Potential equalization (secured in high degree)
- 6 Field device

### Overvoltage protection

- If an overvoltage protection against atmospheric over voltages is required: no other circuits may leave the enclosure during normal operation without additional measures.
- For installations which require overvoltage protection to comply with national regulations or standards, install the device using overvoltage protection (e.g. HAW56x from Endress+Hauser).
- Observe the safety instructions of the overvoltage protection.

Optional specification, ID Nx, Ox = NA  
(Overvoltage protection Type OVP20)

The intrinsically safe input power circuit of the device is isolated from ground. If the device is only equipped with one input, the dielectric strength of the input is at least 290 V<sub>rms</sub>. If the device is equipped with

more than one input, the dielectric strength of each individual input to ground is at least  $290 V_{\text{rms}}$ , and the dielectric strength of the inputs vis-à-vis one another is also at least  $290 V_{\text{rms}}$ .

### Safety instructions: Zone 0

- Associated devices with galvanic isolation between the intrinsically safe and non-intrinsically safe circuits are preferred.
- Only use the device in media to which the silicone rubber potting compound of the electronic insert and the enclosure made of PBT, aluminum or 316L have sufficient durability.
- If there is a risk of dangerous potential differences within Zone 0 (e.g. through the occurrence of atmospheric electricity), implement suitable measures for intrinsically safe circuits in Zone 0.

### Temperature tables

→ Safety Instructions: XA02407F



The safety instructions for temperature tables are available on the Internet: [www.endress.com/Downloads](http://www.endress.com/Downloads)



*Optional specification, ID Nx, Ox = NA  
(Overvoltage protection Type OVP20)*

When using the internal overvoltage protection: Reduce the admissible ambient temperature at the enclosure by 5 K.

*Basic specification, Position 5 = A*

When using the remote display FHX50: Reduce the admissible ambient temperature at the enclosure by 3 K.



Observe the permitted temperature range at the antenna.

### Explanation of how to use the temperature tables



Unless otherwise indicated, the positions always refer to the basic specification.

1st column: Position 5 = A, B, ...

2nd column: Position 3 = A, B, ..

- (1): 1 channel used
- (2): 2 channels used

3rd column: Temperature classes T6 (85 °C) to T1 (450 °C)


Column P1 to P6: Position (temperature value) on the axes of the derating

- $T_a$ : Ambient temperature in °C
- $T_p$ : Process temperature in °C




Column P6 is only relevant for version B of the derating.

Example table

|  = C | (1)  | P1             |                | P2             |                | P3             |                | P4             |                | P5             |                | P6             |                |
|---------------------------------------------------------------------------------------|------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
|                                                                                       |      | T <sub>p</sub> | T <sub>a</sub> | T <sub>p</sub> | T <sub>a</sub> | T <sub>p</sub> | T <sub>a</sub> | T <sub>p</sub> | T <sub>a</sub> | T <sub>p</sub> | T <sub>a</sub> | T <sub>p</sub> | T <sub>a</sub> |
|                                                                                       | E, G | T6             | -40            | 60             | 60             | 60             | 85             | 54             | 85             | -40            | -40            | -              | -              |
|                                                                                       |      | T5             | -40            | 75             | 75             | 75             | 100            | 69             | 100            | -40            | -40            | -              | -              |
|                                                                                       |      | T4             | -40            | 80             | 80             | 80             | 135            | 68             | 135            | -40            | -40            | -              | -              |

Example diagrams of possible deratings



A0022717

Connection data

Optional specification, ID Nx, Ox = NA  
(Overvoltage protection Type OVP20)  
When using the internal overvoltage protection: No changes to the connection values.

Ex ia

Power supply and signal circuit with protection type: intrinsic safety  
Ex ia IIC, Ex ia IIB.

| Terminal 1 (+), 2 (-)                             |                         | Terminal 3 (+), 4 (-)                             |
|---------------------------------------------------|-------------------------|---------------------------------------------------|
| FISCO                                             | Entity                  | Switch output (PFS)                               |
| U <sub>i</sub> = 17.5 V                           | U <sub>i</sub> = 30 V   | U <sub>i</sub> = 30 V                             |
| I <sub>i</sub> = 550 mA                           | I <sub>i</sub> = 300 mA | I <sub>i</sub> = 300 mA                           |
| P <sub>i</sub> = 5.5 W                            | P <sub>i</sub> = 1.2 W  | P <sub>i</sub> = 1 W                              |
| effective inner inductance L <sub>i</sub> = 10 µH |                         | effective inner inductance L <sub>i</sub> = 0     |
| effective inner capacitance C <sub>i</sub> = 5 nF |                         | effective inner capacitance C <sub>i</sub> = 6 nF |

Service interface (CDI)

Taking the following values into consideration, the device can be connected to the certified Endress+Hauser FXA291 service tool or a similar interface:

| Service interface                                                                                                                           |      |      |      |      |      |      |      |      |      |      |       |       |       |  |
|---------------------------------------------------------------------------------------------------------------------------------------------|------|------|------|------|------|------|------|------|------|------|-------|-------|-------|--|
| U <sub>i</sub> = 7.3 V<br>effective inner inductance L <sub>i</sub> = negligible<br>effective inner capacitance C <sub>i</sub> = negligible |      |      |      |      |      |      |      |      |      |      |       |       |       |  |
| U <sub>o</sub> = 7.3 V<br>I <sub>o</sub> = 100 mA<br>P <sub>o</sub> = 160 mW                                                                |      |      |      |      |      |      |      |      |      |      |       |       |       |  |
| L <sub>o</sub> (mH) =                                                                                                                       | 5.00 | 2.00 | 1.00 | 0.50 | 0.20 | 0.15 | 0.10 | 0.05 | 0.02 | 0.01 | 0.005 | 0.002 | 0.001 |  |
| C <sub>o</sub> (µF) <sup>1)</sup> =                                                                                                         | 0.73 | 1.20 | 1.60 | 2.00 | 2.60 | -    | 3.20 | 4.00 | 5.50 | 7.30 | 10.00 | 12.70 | 12.70 |  |
| C <sub>o</sub> (µF) <sup>2)</sup> =                                                                                                         | -    | 0.49 | 0.90 | 1.40 | -    | 2.00 | -    | -    | -    | -    | -     | -     | -     |  |

1) Values according to PTB "ispark" program

2) Values according to IEC/EN 60079-25, Annex C or equivalent national standards

---



71683406

[www.addresses.endress.com](http://www.addresses.endress.com)

---