

# Technical Information

## Liquistation CSF39

Automatic stationary sampler for liquid media, self-draining; integrated controller with up to two measuring channels and optional digital Memosens technology



### Applications

Liquistation CSF39 is a stationary sampler designed for the fully automated sampling, defined distribution, and temperature-controlled storage of liquid media. The standard version has two 0/4 to 20 mA analog inputs, two binary inputs and two binary outputs. Thanks to the modular platform concept, the CSF39 can be quickly and easily modified to create a measuring station.

- Communal and industrial wastewater treatment plants
- Laboratories and water management offices
- Monitoring of liquid media in industrial processes

### Your benefits

- Four different kinds of housing material
- Two-door housing for reliable sample temperature regulation
- Air circulation in both the upper and lower enclosure
- Fast menu guidance, navigator and large display
- Practice-oriented programming
- Functionality can be extended by installing modular electronic components
- Integrated data logger for recording measured values
- Service interface for data transmission
- Optional battery backup system ensures uninterrupted operation if power fails

## Table of contents


<b>Function and system design</b> . . . . .	<b>3</b>	<b>Process</b> . . . . .	<b>23</b>
Device principle . . . . .	3	Medium temperature range . . . . .	23
Sampling unit . . . . .	6	Process pressure range . . . . .	23
Equipment architecture . . . . .	11	Medium properties . . . . .	23
Communication and data processing . . . . .	12	Process connection . . . . .	24
Dependability . . . . .	13		
<b>Input</b> . . . . .	<b>15</b>	<b>Mechanical construction</b> . . . . .	<b>25</b>
Measured variables . . . . .	15	Dimensions . . . . .	25
Measuring ranges . . . . .	15	Weight . . . . .	25
Types of input . . . . .	15	Materials . . . . .	25
Binary input, passive . . . . .	16	<b>Operability</b> . . . . .	<b>27</b>
Temperature input . . . . .	16	Operating concept . . . . .	27
Analog input, passive/active . . . . .	16	Display . . . . .	27
		Local operation . . . . .	28
<b>Output</b> . . . . .	<b>16</b>	Remote operation . . . . .	28
Output signal . . . . .	16	Communication . . . . .	30
Communication . . . . .	16	Software . . . . .	30
Current outputs, active . . . . .	16		
Relay outputs . . . . .	18	<b>Certificates and approvals</b> . . . . .	<b>31</b>
<b>Protocol-specific data</b> . . . . .	<b>18</b>	<b>Ordering information</b> . . . . .	<b>32</b>
HART . . . . .	18	Product page . . . . .	32
Modbus RS485 . . . . .	18	Product Configurator . . . . .	32
Modbus TCP . . . . .	19	Scope of delivery . . . . .	32
EtherNet/IP . . . . .	19		
Web server . . . . .	19	<b>Accessories</b> . . . . .	<b>33</b>
		Measuring cable . . . . .	33
<b>Power supply</b> . . . . .	<b>19</b>	Sensors . . . . .	34
Supply voltage . . . . .	19		
Power consumption . . . . .	20		
Electrical connection . . . . .	20		
Cable entries . . . . .	20		
Mains fuse . . . . .	20		
Power supply failure . . . . .	20		
<b>Performance characteristics</b> . . . . .	<b>20</b>		
Sampling methods . . . . .	20		
Dosing volume . . . . .	20		
Dosing accuracy . . . . .	20		
Repeatability . . . . .	20		
Intake speed . . . . .	20		
Suction height . . . . .	20		
Hose length . . . . .	20		
Temperature control . . . . .	21		
<b>Mounting</b> . . . . .	<b>22</b>		
Mounting instructions . . . . .	22		
Mounting conditions . . . . .	22		
<b>Environment</b> . . . . .	<b>23</b>		
Ambient temperature range . . . . .	23		
Storage temperature . . . . .	23		
Electrical safety . . . . .	23		
Relative humidity . . . . .	23		
Degree of protection . . . . .	23		
Electromagnetic compatibility (EMC) . . . . .	23		

## Function and system design

### Device principle

### Mode of operation with a vacuum pump


Sampling takes place in four steps:



A0022647

1. Blow clear
  - ↳ The vacuum pump blows the suction line clear via the dosing system.
2. Intake
  - ↳ The "Airmanager" (pneumatic control unit) switches the air path of the vacuum pump to "intake". The sample is drawn into the dosing beaker until it reaches the conductivity probes of the dosing system.
3. Dose
  - ↳ The intake process ends. Depending on the position of the dosing tube (item D), the excess sample liquid flows back to the sampling point.
4. Drain
  - ↳ The hose clamp is opened and the sample is drained into the sample bottle.

### Dosing system with conductive sample sensor



A0022663


#### 1 Conductive dosing system

- 1 Conductivity sensor 1 (common electrode)
- 2 Conductivity sensor 2 (safety electrode)
- 3 Conductivity sensor 3 (standard electrode)
- 4 Insulation
- 5 Measuring jug (plastic version with graduated scale or glass)
- 6 Graduated dosing tube, white and blue scale

### Level detection principle

When the sample is drawn in, the sample level reaches conductivity sensors 1 and 3. As a result, the system detects that the measuring jug is filled and the intake process is stopped. If sensor 3 fails or is very dirty, a safety shutdown is performed by conductivity sensor 2. This patented sample detection method prevents vacuum pump failure due to flooding and enables predictive maintenance information to be displayed.

## Dosing system with capacitance sample sensor



A0024340


 2 *Capacitance dosing system*

- 1 *Hose connection for vacuum pump*
- 2 *Measuring jug with graduated scale*
- 3 *Graduated dosing tube, white and blue scale*
- 4 *Capacitance level sensor*

**Level detection principle**


When the level of medium in the measuring jug changes, the capacitance of a capacitor partially formed by the liquid also changes.

The capacitance sensor ensures rapid sample detection in foaming media, media with a high fat content and media with a conductivity  $<30 \mu\text{S}/\text{cm}$ . Only capacitance level detection is possible in the latter type of media.

 **Sample dosing without/with pressure**

Sample dosing without pressure is the (factory) setting for all standard applications in which the sample medium is taken from an open channel or a gravity line. The excess sample can flow back under atmospheric pressure. Sample dosing with pressure is selected for applications involving a low suction height, small sampling volumes or high-viscosity samples. In these cases, the sample medium cannot flow back on its own. The excess sample is forced out of the measuring jug under pressure and back to the sampling point. The sample volume is set by adjusting the dosing tube. The white "A" scale applies if dosing without pressure, and the blue "B" scale applies if dosing with pressure.

**Mode of operation with a peristaltic pump**




A0050001

3 Sampling steps with a peristaltic pump

**Sampling takes place in three steps:**

1. Rinse
  - ↳ The peristaltic pump runs in reverse and forces medium back to the sampling point.
2. Intake
  - ↳ The peristaltic pump runs forward and draws in medium. If the medium detection system detects the sample, the pump is controlled by the flow and the specified sample volume is calculated automatically.
3. Drain
  - ↳ The pump runs in reverse again and forces the medium back to the sampling point.


One advantage for obtaining a representative sample is the possibility of rinsing the suction line several times: Medium is initially drawn in until the medium detection function responds, then the pump switches and forces the medium back to the sampling point. This process can be repeated a maximum of three times. The sample is then taken as described.



A0050003

4 Peristaltic pump

- 1 Pump tube
- 3 Pump rollers
- 4 Medium detection system (patented)



A0024343

5 Peristaltic pump

- 1 Pump tube
- 2 Safety switch (optional)
- 3 Pump rollers
- 4 Medium detection system (patented)


The pump rollers deform the hose, thereby causing a negative pressure and the suction effect. The medium detection system is based on a pressure sensor which detects the difference between a pipe that is filled and not filled. Thanks to a patented process for automatically detecting the suction height, the user does not need to enter the suction height or suction line length. The self-learning software guarantees a constant sample volume. An optional safety switch integrated in the pump housing immediately switches off the pump when the pump is opened (recommended if third-party staff are performing maintenance work).

## Sampling unit

### Sampler Liquistation CSF39

A complete sampling unit comprises:


- Controller with display, soft keys and navigator
- Vacuum or peristaltic pump for sampling
- PE sample bottles, self-emptying
- Sampling chamber temperature regulator (optional) for safe sample storage
- Suction line with suction head



A0024519

6 Example of a Liquistation CSF39, version with vacuum pump

- 1 Controller
- 2 Window (optional)
- 3 Dosing compartment door
- 4 Suction line connection
- 5 Sampling chamber door
- 6 Cleaning nozzle
- 7 Sampling container, 2 x 1500 ml, PE
- 8 Drain hose
- 9 Distribution arm
- 10 Vacuum system, e.g. Dosing system with conductive sample sensor



- 1 Controller
- 2 Window (optional)
- 3 Dosing compartment door
- 4 Suction line connection
- 5 Sampling chamber door
- 6 Cleaning nozzle
- 7 Sampling container, 2 x 15000 ml, PE
- 8 Drain hose
- 9 Distribution arm
- 10 Peristaltic pump

A0024521

7 Example of a Liquistation, version with peristaltic pump


## Sampler with online measurement

**i** The following overview shows examples of the design and layout of a measuring system. Other sensors and assemblies can be ordered for conditions specific to your application. See Accessories section and also --> [www.endress.com/products](http://www.endress.com/products)

### Measuring point

A complete measuring system with online measurement consists of:


- Liquistation CSF48 sampler
- Sensors with Memosens technology
- Immersion or flow assemblies to suit the sensors used



A0029246

### Nitrate

- Liquistation CSF48 sampler
- Sensors with Memosens technology
- Immersion or flow assemblies to suit the sensors used



A0024327


### Conductivity

Inductive conductivity measurement

- Flexdip CYA112 immersion assembly
- Indumax CLS50D sensor with fixed cable

Conductive conductivity measurement


- Flexdip CYA112 immersion assembly
- Condumax CLS15D sensor



A0024329

### Oxygen

- Flexdip CYA112 immersion assembly
- Flexdip CYH112 holder
- Sensor
  - Oxymax COS61D (optical) with fixed cable,
  - Oxymax COS51D (amperometric) cable CYK10




A0024332

Figure: CYA112 with COS61D

### Turbidity


- Flexdip CYA112 immersion assembly
- Spray head CUR4 (optional)
- Turbimax CUS51D sensor with fixed cable



A0024333


### pH value or ORP

- Retractable assembly Cleanfit CPA471
- Orbisint CPS11D, CPS12D sensor
- Measuring cable CYK10




A0024336

- Flowfit CUA250 flow assembly
- Turbimax CUS51D sensor with fixed cable



A0024334

- Flexdip CYA112 immersion assembly
- Orbisint CPS12D, CPS11D sensor
- Measuring cable CYK10




A0024335

### Sample distribution

The sampler offers a bottle version with 2x 15000 ml PE vessels with a self-emptying function and automatic cleaning. The vessels are easy to change or replace without the need for tools.



**Sampling control**




- a. Flow curve
- b. **Time-paced sampling CTCV**  
A constant sample volume (e.g. 50 ml) is taken at regular intervals (e.g. every 5 min).
- c. **Flow-paced sampling VTCV**  
A constant sample volume is taken at variable intervals (depending on the inflow volume).
- d. **Time/flow-paced sampling CTVV**  
A variable sample volume (the sample volume depends on the inflow) is taken at regular intervals (e.g. every 10 min).

**i** Only possible for version with peristaltic pump.

8 Sampling control

**Intake speed with different suction lines**



9 Intake speed in m/s (ft/s) with suction height in m (ft)

- a Intake speed as per Ö 5893; US EPA
- b Intake speed as per EN 25667, ISO 5667
- 1 ID 10 mm (3/8 in) vacuum pump
- 2 ID 13 mm (1/2 in) vacuum pump
- 3 ID 10 mm (3/8 in) peristaltic pump
- 4 ID 16 mm (5/8 in) vacuum pump
- 5 ID 19 mm (3/4 in) vacuum pump

**Sample temperature regulation (optional)**

The temperature of the sample compartment can be adjusted using the controller. The factory setting is 4 °C (39 °F). The current temperature is shown on the display and can be recorded in the internal data logger.

A temperature sensor for measuring individual sample temperatures can be ordered as an option.

The vaporizer and defrost heater are integrated in a special housing such that they are protected against corrosion and damage. The compressor and the condenser are located in the upper section of the sampler. They can be easily accessed by removing the upper rear panel (for maintenance purposes).



A0024355

 10 Cooling system

### Sampler housing


Pay attention to the installation conditions in the "Installation" section and the information on the materials of the different housing types in the "Mechanical construction" section.

#### NOTICE

**Plastic polystyrene VO can discolor when exposed to direct sunlight.**

In the case of stainless steel housings, the frame around the window can discolor if exposed directly to sunlight.

- ▶ For outdoor use without a weather protection cover, the use of Plastic ASA+PC VO is recommended. The functionality is not affected by the discoloration.



11 Slot and port assignment of hardware and presentation on the display


**The electronics configuration follows a modular concept:**

- There are several slots for electronics modules. These are referred to as "slots".
  - These slots are numbered consecutively in the housing. Slots 0 and 1 are always reserved for the base module.
  - In addition there are also inputs and outputs for the control module. These slots are labeled "S".
  - Each electronics module has one or more inputs and outputs or relays. Here they are all collectively known as "ports".
  - Ports are consecutively numbered per electronics module and are recognized automatically by the software.
  - Outputs and relays are named according to their function, e.g. "current output", and are displayed in ascending order with the slot and port numbers.
- Example:  
 "Current output 2:1" shown on the display means: slot 2 (e.g. AOR module) : port 1 (current output 1 of the AOR module)
- Inputs are assigned to measuring channels in the ascending order of "slot:port number"
- Example:  
 "CH1: 1:1" shown on the display means:  
 Slot 1 (base module) : port 1 (input 1) is channel 1 (CH1).

---

**Communication and data processing****Communication protocols:**

- Fieldbus systems
  - HART
  - Modbus TCP or RS485
  - PROFINET
  - EtherNet/IP
- Configuration via Ethernet

 Only one type of fieldbus communication can ever be active. The last activation code entered decides which bus is used.

The device drivers available make it possible to perform a basic setup and display measured values and diagnostics information via the fieldbus. A full device configuration via the fieldbus is not possible.

**Extension module ETH and current outputs**

Communication via Ethernet or EtherNet/IP

A maximum of 4 current outputs can be used in parallel.

## Dependability

## Reliability

### Memosens technology



Memosens makes your measuring point safer and more reliable:

- Non-contact, digital signal transmission enables optimum galvanic isolation
- No contact corrosion
- Completely watertight
- Laboratory sensor calibration possible, thus increasing measured value availability
- Predictive maintenance thanks to recording of sensor data, e.g.:
  - Total hours of operation
  - Hours of operation with very high or very low measured values
  - Hours of operation at high temperatures
  - Number of steam sterilizations
  - Sensor condition



A0024356

### Sensor check system (SCS)

The sensor check system (SCS) monitors the high impedance of the pH glass. An alarm is triggered if a minimum impedance value is undershot or a maximum impedance is exceeded.

- Glass breakage is the main reason for a drop in high impedance values.
- The causes of increasing impedance values are:
  - Dry sensor
  - Worn pH glass membrane

### Process check system (PCS)

The process check system (PCS) checks the measuring signal for stagnation. An alarm is triggered if the measuring signal does not change over a certain period (several measured values).

#### The main causes of stagnating measured values are:

- Sensor fouled or outside the medium
- Sensor defective
- Process error (e.g. through control system)

### Sensor condition check (SCC)

This function monitors the electrode condition and the degree of electrode aging. The status is indicated by the messages "SCC electrode condition bad" or "SCC electrode condition OK". The electrode condition is updated after every calibration.

## Maintainability

### Modular design


The modular sampler can be easily adapted to suit your needs:

- Retrofit extension modules for new or extended range of functions, e.g. current outputs and relays
- Upgrade to fieldbus communication (PROFIBUS DP, Modbus TCP, Modbus RS485, Ethernet, PROFINET for configuration and EtherNet/IP)

### Memory

- Independent, integrated ring memories (FIFO) or stack memories for recording
  - an analog value (e.g. flow, pH value, conductivity)
  - events (e.g. power failure)
  - Sample statistics (e.g. sampling volume, filling times, bottle assignment)
- Program memory: max. 100 programs
- Data logbooks:
  - Adjustable scan time: 1 to 3600 s (1 h)
  - Max. 8 data logbooks
  - 150,000 entries per logbook
  - Graphic display (load curves) or numerical list
- Calibration logbook: max. 75 entries

- Hardware logbook:
  - Hardware configuration and modifications
  - Max. 125 entries
- Version logbook:
  - Including software updates
  - Max. 50 entries
- Operations logbook: max. 250 entries
- Diagnostic logbook: max. 250 entries



A0024359

12 Data logbook: graphic display

### Mathematical functions (virtual process values)

In addition to "real" process values, which are provided by connected physical sensors or analog inputs, mathematical functions can be used to calculate a maximum of 6 "virtual" process values.

#### The "virtual" process values can be:

- Output via a current output or a fieldbus
- Used as a regulating control variable
- Assigned as a measured variable to a limit contactor
- Used as a measured variable to trigger cleaning
- Displayed in user-defined measuring menus

#### The following mathematical functions are possible:

- pH calculation based on two conductivity values according to VGB Standard 405, e.g. in boiler feedwater
- Difference between two measured values from different sources, e.g. for membrane monitoring
- Differential conductivity, e.g. for monitoring the efficiency of ion exchangers
- Degassed conductivity, e.g. for process controls in power plants
- Redundancy to monitor two or three redundant sensors
- rH calculation from the measured values of a pH and an ORP sensor

### FieldCare and Field Data Manager

#### FieldCare


Configuration and asset management software based on FDT/DTM technology

- Complete device configuration when connected via FXA291 and service interface
- Access to a number of configuration parameters and identification, measuring and diagnostic data when connected via HART modem
- Logbooks can be downloaded in CSV format or binary format for the "Field Data Manager" software

#### Field Data Manager

Visualization software and database for measuring, calibration and configuration data

- SQL database which is protected against manipulation
- Functions to import, save and print out logbooks
- Load curves to display measured values
- All the logbooks can be read out and saved online



A0016009

13 Field Data Manager: load curves

### SD card

The exchangeable storage medium enables:

- Quick and easy software updates and upgrades
- Data storage of internal device memory (e.g. logbooks)
- Transfer of complete configurations to a device with an identical setup (backup function)
- Transfer of configurations without the device designation and bus address to devices with an identical setup (copy function)

Endress+Hauser offers industry-approved SD cards as accessories. These memory cards provide maximum data security and integrity.

Other SD cards can also be used. However, Endress+Hauser does not accept any responsibility for the data security of such cards.

### Security

#### Real-time clock

The device has a real-time clock, which is backed up by a button cell in the event of a power failure. This ensures that the device continues to keep the correct time and date if it is restarted and that the time stamp for the logbooks is correct.

#### Data security

All settings, logbooks etc. are stored in a non-volatile memory to ensure that the data are retained even in the event of a disruption to the power supply.

## Input

**Measured variables** → Documentation of the connected sensor

**Measuring ranges** → Documentation of the connected sensor

**Types of input**

- 2 analog inputs
- 2 binary inputs + 2 binary inputs (optional)
- 1 to 4 digital inputs for sensors with Memosens protocol (optional)

---

<b>Binary input, passive</b>	<b>Span</b>
	12 to 30 V, galvanically isolated
	<b>Signal characteristics</b>
	Minimum pulse width: 100 ms
	<b>Signal edge</b>
	Low-high

---

<b>Temperature input</b>	<b>Measuring range</b>
	-30 to 70 °C (-20 to 160 °F)
	<b>Accuracy</b>
	± 0.5 K
	<b>Type of input</b>
	Pt1000

---

<b>Analog input, passive/active</b>	<b>Span</b>
	0/4 to 20 mA, galvanically isolated
	<b>Accuracy</b>
	±0.5 % of measuring range

## Output

---

<b>Output signal</b>	2 binary outputs (standard): Open collector, max. 30 V, 200 mA
----------------------	---

---

<b>Communication</b>	<ul style="list-style-type: none"> <li>▪ 1 service interface</li> <li>▪ Accessible via front panel connection (optional)</li> <li>▪ Commubox FXA291 (accessory) required for communication with the PC</li> </ul>
----------------------	---

---

<b>Current outputs, active</b>	<b>Span</b>
	0 to 23 mA
	2.4 to 23 mA for HART communication
	<b>Signal characteristic</b>
	Linear
	<b>Signal on alarm</b>
	Adjustable, as per NAMUR Recommendation NE 43
	<ul style="list-style-type: none"> <li>▪ In measuring range 0 to 20 mA (HART is not available with this measuring range): Failure current from 0 to 23 mA</li> <li>▪ In measuring range 4 to 20 mA: Failure current from 2.4 to 23 mA</li> <li>▪ Factory setting for failure current for both measuring ranges: 21.5 mA</li> </ul>
	<b>Load</b>
	Max. 500 Ω
<b>Electrical specification</b>	
<i>Output voltage</i>	
Max. 24 V	

---



**Cable specification**

*Cable type*

Recommended: shielded cable

*Cross-section*

Recommended: shielded cable

**Relay outputs****Electrical specification****Relay types**

- 2 x changeover contact, coupled with binary output (optional)
- 1 single-pin changeover contact (alarm relay)

**Maximum load**

- Alarm relay: 0.5 A
- All other relays: 2.0 A

**Relay switching capacity**

*Power unit (Alarm relay)*

Switching voltage	Load (max.)	Switching cycles (min.)
230 V AC, $\cos\Phi = 0.8$ to 1	0.1 A	700,000
	0.5 A	450,000
24 V DC, L/R = 0 to 1 ms	0.1 A	500,000
	0.5 A	350,000

*Relay coupled with binary output*

Switching voltage	Load (max.)	Switching cycles (min.)
230 V AC, $\cos\Phi = 0.8$ to 1	5 A	100,000
24 V DC, L/R = 0 to 1 ms	5 A	100,000

**Protocol-specific data****HART**

Manufacturer ID	11 <sub>h</sub>
Device type	119D <sub>h</sub>
Device revision	001 <sub>h</sub>
Device description files (DD/DTM)	<a href="http://www.endress.com/hart">www.endress.com/hart</a> Device Integration Manager DIM
Device variables	
Supported features	PDM DD, AMS DD, DTM,

**Modbus RS485**

Protocol	RTU/ASCII
Function codes	03, 04, 06, 08, 16, 23
Broadcast support for function codes	06, 16, 23
Output data	16 measured values (value, unit, status), 8 digital values (value, status)
Input data	4 setpoints (value, unit, status), 8 digital values (value, status), diagnostic information
Supported features	Address can be configured using switch or software

<b>Modbus TCP</b>	TCP port	502
	TCP connections	3
	Protocol	TCP
	Function codes	03, 04, 06, 08, 16, 23
	Broadcast support for function codes	06, 16, 23
	Output data	16 measured values (value, unit, status), 8 digital values (value, status)
	Input data	4 setpoints (value, unit, status), 8 digital values (value, status), diagnostic information
	Supported features	Address can be configured using DHCP or software

<b>EtherNet/IP</b>	Log	EtherNet/IP		
	ODVA certification	Yes		
	Device profile	Generic device (product type: 0x2B)		
	Manufacturer ID	0x049E <sub>h</sub>		
	Device type ID	0x109		
	Polarity	Auto-MIDI-X		
	Connections	CIP	12	
		I/O	6	
		Explicit message	6	
		Multicast	3 consumers	
	Minimum RPI	100 ms (default)		
	Maximum RPI	10000 ms		
	System integration	EtherNet/IP	EDS	
		Rockwell	Add-on-Profile Level 3, Faceplate for Factory Talk SE	
IO data	Input (T → O)	Device status and diagnostic message with highest priority Measured values: <ul style="list-style-type: none"> <li>▪ 16 AI (analog input) + Status + Unit</li> <li>▪ 8 DI (discrete input) + Status</li> </ul>		
	Output (O → T)	Actuating values: <ul style="list-style-type: none"> <li>▪ 4 AO (analog output) + status + unit</li> <li>▪ 8 DO (discrete output) + Status</li> </ul>		


**Web server** The web server enables full access to the device configuration, measured values, diagnostic messages, logbooks and service data via standard WiFi/WLAN/LAN/GSM or 3G routers with a user-defined IP address.

TCP port	80
Supported features	<ul style="list-style-type: none"> <li>▪ Remote-controlled device configuration</li> <li>▪ Save/restore device configuration (via SD card)</li> <li>▪ Logbook export (file formats: CSV, FDM)</li> <li>▪ Access to web server via DTM or Internet Explorer</li> </ul>


## Power supply

**Supply voltage**

- 100 to 120/200 to 240 V AC ±10 %, 50/60 Hz
- 24 V DC +15/-9 %

<b>Power consumption</b>	<ul style="list-style-type: none"> <li>▪ Version with vacuum pump: 290 VA</li> <li>▪ Version with peristaltic pump: 290 VA</li> </ul>
<b>Electrical connection</b>	See the "Electrical connection" section ()
<b>Cable entries</b>	<p>Depending on version:</p> <ul style="list-style-type: none"> <li>▪ 1 x M25, 7 x M20 cable gland</li> <li>▪ 1 x M25, 1 x M20 cable gland</li> </ul> <p>Permitted cable diameter:</p> <ul style="list-style-type: none"> <li>▪ M20x1.5 mm: 7 to 13 mm (0.28 to 0.51")</li> <li>▪ M25x1.5 mm: 9 to 17 mm (0.20 to 0.67")</li> </ul>
<b>Mains fuse</b>	<ul style="list-style-type: none"> <li>▪ T3.15A (for 230V power supply)</li> <li>▪ T10A (for 24V power supply)</li> <li>▪ For version with cCSAus approval: T4A (for cooling module)</li> </ul>
<b>Power supply failure</b>	<p>Power supply (optional): 2 x 12 V, 7.2 Ah, with additional charge controller</p> <p> Replace the rechargeable batteries with type Panasonic LC-R127R2PG1.</p> <p>Real-time clock: lithium battery, type CR2032</p>

## Performance characteristics

<b>Sampling methods</b>	<p><b>Vacuum pump:</b></p> <ul style="list-style-type: none"> <li>▪ Time-paced</li> <li>▪ Flow-paced</li> </ul> <p><b>Peristaltic pump:</b></p> <ul style="list-style-type: none"> <li>▪ Time-paced</li> <li>▪ Flow-paced</li> <li>▪ Flow proportional sampling/time override (CTVV)</li> </ul>
<b>Dosing volume</b>	<p><b>Vacuum pump:</b> 20 to 350 ml (0.7 to 12 fl.oz.)</p> <p><b>Peristaltic pump:</b> 10 to 10000 ml (0.3 to 340 fl.oz.)</p> <p> The dosing accuracy and the repeatability of a sample volume &lt; 20 ml (0.7 fl.oz) can vary, depending on the specific application.</p>
<b>Dosing accuracy</b>	<ul style="list-style-type: none"> <li>▪ <b>Vacuum pump:</b> ± 5 ml (0.17 fl.oz.) or 5 % of the set volume</li> <li>▪ <b>Peristaltic pump:</b> ± 5 ml (0.17 fl.oz.) or 5 % of the set volume</li> </ul>
<b>Repeatability</b>	5 %
<b>Intake speed</b>	<p>&gt; 0.5 m/s (&gt; 1.6 ft/s) for ≤ 13 mm (1/2 in) ID, as per EN 25667, ISO 5667, CEN 16479-1</p> <p>&gt; 0.6 m/s (&gt; 1.9 ft/s) for 10 mm (3/8 in) ID, as per Ö 5893; US EPA</p>
<b>Suction height</b>	<ul style="list-style-type: none"> <li>▪ <b>Vacuum pump:</b> Max. 6 m (20 ft) or max. 8 m (26 ft), depending on the version</li> <li>▪ <b>Peristaltic pump:</b> Max. 8 m (26 ft)</li> </ul>
<b>Hose length</b>	Max. 30 m (98 ft)

**Temperature control**

**Temperature sensors:**


- Sampling compartment temperature
- Sample temperature (optional)
- Outside temperature (optional)

**Cooling module:**

- Sample temperature range: 2 to 20 °C (36 to 68 °F)  
Factory setting: 4 °C (39 °F)
- Automatic defrost system
- Cooling rate in accordance with Ö 5893 (Austrian standard):  
4 liters of water at 20 °C (68 °F) cool down to 4 °C (39 °F) in less than 210 minutes
- Temperature constancy of sample at 4 °C (39 °F) at an operating temperature range of -15 to 40 °C (5 to 105 °F)

## Mounting

### Mounting instructions




A0024406

14 Foundation plan. Unit of measurement mm (in)

- A Fasteners (4 x M10)
- B Cable inlet
- C Outlet for condensate and overflow > DN 50
- D Sample supply from below > DN 80
- Dimensions of Liquistation

### Mounting conditions



A0024411

15 Liquistation mounting conditions

#### Mounting conditions

Route the suction line with a downward gradient to the sampling point.

Never mount the sampler in a place where it is exposed to aggressive gases.

**Mounting conditions**

Avoid siphoning effects in the suction line.

Do not route the suction line with an upward gradient to the sampling point.

Note the following when erecting the device:

- Erect the device on a level surface.
- Connect the device securely to the surface at the fastening points.
- Protect the device against additional heating (e.g. heaters or direct sunlight).
- Protect the device against mechanical vibrations.
- Protect the device against strong magnetic fields.
- Make sure air can circulate freely at the side panels of the cabinet. Do not mount the device directly against a wall. Allow at least 150 mm (5.9 in.) from the wall to the left and right.
- Do not erect the device directly above the inlet channel of a wastewater treatment plant.

## Environment

<b>Ambient temperature range</b>	With cooling module:	-20 to 40 °C (0 to 104 °F)
	Without cooling module:	0 to 40 °C (32 to 104 °F)
	With ASA+PC or stainless steel housing:	-20 to 40 °C (0 to 104 °F)
	With plastic polystyrene housing:	0 to 40 °C (32 to 104 °F)
<b>Storage temperature</b>	-20 to 60 °C (-4 to 140 °F)	
<b>Electrical safety</b>	In accordance with EN 61010-1, protection class I, environment ≤ 2000 m (6500 ft) above MSL. The device is designed for pollution degree 2.	
<b>Relative humidity</b>	10 to 95%, not condensing	
<b>Degree of protection</b>	<ul style="list-style-type: none"> <li>■ Front dosing compartment: IP 54</li> <li>■ Rear dosing compartment: IP 33</li> <li>■ Front panel with display (internal): IP 65</li> <li>■ Sample compartment: IP 54</li> </ul> <p>The IP protection ratings listed above apply for individual sections of the overall device. The resulting degree of protection for the overall device is IP33.</p>	
<b>Electromagnetic compatibility (EMC)</b>	Interference emission and interference immunity as per EN 61326-1:2013, Class A for Industry	

## Process

<b>Medium temperature range</b>	2 to 50 °C (36 to 122 °F)	
<b>Process pressure range</b>	<ul style="list-style-type: none"> <li>■ Unpressurized, open channel (unpressurized sampling)</li> <li>■ Max. 0.8 bar piping (only with shutoff/inlet valve)</li> </ul>	
<b>Medium properties</b>	<p><b>Vacuum pump</b></p> <p>Capacitance level measurement used for:</p> <ul style="list-style-type: none"> <li>■ Sample media has to be free of abrasive substances.</li> <li>■ Media that tend to create a lot of foam or contain fats and grease</li> <li>■ Media with a conductivity &lt; 30 µS/cm</li> </ul>	

**Peristaltic pump**

Sample media has to be free of abrasive substances.



Pay attention to the material compatibility of the wetted parts.

---

**Process connection****▪ Vacuum pump:**

Intake hose ID 10 mm (3/8 in), 13 mm (1/2 in), 16 mm (5/8 in) or 19 mm (3/4 in)


**▪ Peristaltic pump:**

Intake hose ID 10 mm (3/8 in)



## Mechanical construction


### Dimensions



A0024494

16 Dimensions of Liquistation, plastic version, with stand. Unit of measurement mm (in)

A Suction line connection



A0024495

17 Dimensions of Liquistation, stainless steel version, with stand. Unit of measurement mm (in)

A Suction line connection

### Weight

Sampler version	Weight
Plastic version without refrigeration	91 kg (201 lbs)
Plastic version with refrigeration	101 kg (223 lbs)
Stainless steel version with stand and refrigeration	146 kg (322 lbs)
Stainless steel version with refrigeration	125 kg (276 lbs)


### Materials



Plastic polystyrene VO can change color when exposed to direct sunlight. For outdoor use without a weather protection cover, the use of Plastic ASA+PC VO is recommended. The functionality is not affected by the discoloration.

Non-wetted parts	
Cabinet housing	<p><b>Plastic polystyrene V0</b> For standard applications in wastewater treatment plants and environmental monitoring</p> <p><b>Plastic ASA+PC V0</b> For industrial wastewater treatment plants with an aggressive atmosphere</p> <p><b>Stainless steel V2A (1.4301)</b> For standard applications in wastewater treatment plants and environmental monitoring</p> <p><b>Stainless steel V4A (1.4571)</b> For industrial wastewater treatment plants with an aggressive atmosphere</p>
Sample compartment inner lining	Plastic PP
Window	Safety glass, coated
Insulation	Plastic EPS "Neopor®"

Wetted parts	Vacuum pump	Peristaltic pump
Dosing tube	Plastic PP	-
Measuring jug cover	Plastic PP	-
Conductivity sensors	Stainless steel V4A (1.4404)	-
Conductivity sensors	Stainless steel V4A (1.4404)	-
Measuring jug	PMMA, glass (depending on version)	-
Dosing system outflow hose	Silicone	-
Pump tube	-	Silicone
Process seal	-	-
Distribution arm	Plastic PP	
Distribution arm cover	Plastic PE	
Distribution plate	Plastic PS	
Composite container/bottles	Plastic PE, glass (depending on version)	
Intake hose	Plastic PVC, EPDM (depending on version)	
Hose connection	Plastic PP	
Rinse connection	-	-

 Choose process seal depending on the application. Viton is recommended for standard applications involving watery samples.

Vacuum pump only	
Pneumatic hoses	Silicone
Air Manager housing	PC
Air Manager sealing plate	Silicone
Pump head	Aluminum, anodized
Pump membrane	EPDM

## Operability

### Operating concept


The simple and structured operating concept sets new standards:

- Intuitive operation with the navigator and soft keys
- Fast configuration of application-specific measurement options
- Easy configuration and diagnosis thanks to plain-text display
- All languages that can be ordered are available in every device



A0024560

18 Easy operation




A0024443-EN

19 Plain-text menu


### Display

Graphic display:

- Resolution: 240 x 160 pixel
- Back light with switch-off function
- Red display background for alarms alerts users to errors
- Transflective display technology for maximum contrast even in bright environments
- User-definable measuring menus mean you can always keep track of the values that are important for your application.



20 Example of program setup



21 Example of measuring menu

## Local operation




A0049186

- LCD, illuminated (with red background in the event of an error)
- 160 x 240 pixels
- 4 operating keys (soft key function) and navigator (jog/shuttle and press/hold function)
- Menu-guided operation

## Remote operation

## Via HART (e.g. via HART modem and FieldCare)




A0039620

22 HART using modem

- 1 Device module Base2-E: current output 1 with HART
- 2 HART modem for connection to PC, e.g. Commubox FXA191 (RS232) or FXA195 <sup>1)</sup> (USB)
- 3 HART handheld terminal

<sup>1)</sup> Switch position "on" (substitutes the resistor)

Via PROFIBUS DP




A0039617

23 PROFIBUS DP

T Terminating resistor

Via Modbus RS485




A0039615

24 Modbus RS485

T Terminating resistor

## Via Ethernet: web server/Modbus TCP/PROFINET/Ethernet/IP



A0039616

25 Modbus TCP or Ethernet/IP or PROFINET

### Communication

- 1 service interface
- Optionally on front panel
- Commubox FXA291 (accessory) required for communication with the PC

### Software

#### Field Data Manager

- Standardized user interface under Windows®
- Reading data out of internal data memory with measured flow rate, sampling volume taken etc.

#### FieldCare

- Storage of device settings in a database
- Parameter configuration

## Certificates and approvals

Current certificates and approvals that are available for the product can be selected via the Product Configurator at [www.endress.com](http://www.endress.com):

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Configuration**.

---


## Ordering information

---

**Product page**[www.endress.com/CSF39](http://www.endress.com/CSF39)

---

**Product Configurator**

1. **Configure:** Click this button on the product page.
  2. Select **Extended selection**.
    - ↳ The Configurator opens in a separate window.
  3. Configure the device according to your requirements by selecting the desired option for each feature.
    - ↳ In this way, you receive a valid and complete order code for the device.
  4. **Apply:** Add the configured product to the shopping cart.
-  For many products, you also have the option of downloading CAD or 2D drawings of the selected product version.
5. **Show details:** Open this tab for the product in the shopping cart.
    - ↳ The link to the CAD drawing is displayed. If selected, the 3D display format is displayed along with the option to download various formats.
- 

**Scope of delivery**

The scope of delivery comprises:

- 1 Liquistation CSF39 with:
  - The ordered bottle configuration
  - Optional hardware
- Accessories kit
  - For peristaltic or vacuum pump:  
Hose adapter for suction line with various angles (straight, 90°), Allen screw (for version with vacuum pump only)
- 1 printed copy of the Brief Operating Instructions in the language ordered
- Optional accessories



## Accessories

The following are the most important accessories available at the time this documentation was issued.

Listed accessories are technically compatible with the product in the instructions.

1. Application-specific restrictions of the product combination are possible.  
Ensure conformity of the measuring point to the application. This is the responsibility of the operator of the measuring point.
2. Pay attention to the information in the instructions for all products, particularly the technical data.
3. For accessories not listed here, please contact your Service or Sales Center.

Order no.	Complete suction line
71111233	Suction line ID 10 mm (3/8"), PVC, reinforced fabric, length 10 m (33 ft), suction head V4A
71111234	Suction line ID 10 mm (3/8"), EPDM, length 10 m (33 ft), suction head V4A
71111235	Suction line ID 13 mm (1/2"), PVC, reinforced spiral wire, length 10 m (33 ft), suction head V4A
71111236	Suction line ID 13 mm (1/2"), EPDM, length 10 m (33 ft), suction head V4A
71111237	Suction line ID 16 mm (5/8"), PVC, reinforced spiral wire, length 10 m (33 ft), suction head V4A
71111238	Suction line ID 16 mm (5/8"), EPDM, length 10 m (33 ft), suction head V4A
71111239	Suction line ID 19 mm (3/4"), PVC, reinforced spiral wire, length 10 m (33 ft), suction head V4A
71111240	Suction line ID 19 mm (3/4"), EPDM, length 10 m (33 ft), suction head V4A

Order no.	Terminated hose: vacuum pump
71111188	Dosing hose to distributor, 2 pcs, material: silicon
71111189	Dosing hose to distributor, 25 pcs, material: silicon

Order no.	Terminated hose: peristaltic pump
71111191	Pump tubing, 2 pcs; material: silicon
71111192	Pump tubing, 25 pcs; material: silicon

Order no.	Communication; software
71239104	Activation code: Chemoclean Plus
71110815	SD card, 1 GB, Industrial Flash Drive
51516983	Commubox FXA291 + FieldCare Device Setup
71129799	Field Data Manager software; 1 license, analysis report
71127100	SD card with Liquiline Firmware, 1 GB, Industrial Flash Drive
71128428	Activation code for digital HART communication
71367524	Activation code for Heartbeat Verification and Monitoring

### Measuring cable

#### Memosens data cable CYK10

- For digital sensors with Memosens technology
- Product Configurator on the product page: [www.endress.com/cyk10](http://www.endress.com/cyk10)



Technical Information TI00118C

**Measuring cable CYK81**

- Unterminated cable for extending sensor cables (e.g. Memosens, CUS31/CUS41)
- 2 x 2 cores, twisted with shielding and PVC sheath (2 x 2 x 0.5 mm<sup>2</sup> + shielding)
- Sold by meter, Order No.: 51502543

**Sensors****Glass electrodes****Orbisint CPS11D**

- pH sensor for process technology
- With dirt-repellent PTFE diaphragm
- Product Configurator on the product page: [www.endress.com/cps11d](http://www.endress.com/cps11d)



Technical Information TI00028C

**Memosens CPS31D**

- pH electrode with gel-filled reference system with ceramic diaphragm
- Product Configurator on the product page: [www.endress.com/cps31d](http://www.endress.com/cps31d)



Technical Information TI00030C

**Ceraliquid CPS41D**

- pH electrode with ceramic junction and KCl liquid electrolyte
- Product Configurator on the product page: [www.endress.com/cps41d](http://www.endress.com/cps41d)



Technical Information TI00079C

**Ceragel CPS71D**

- pH electrode with reference system including ion trap
- Product Configurator on the product page: [www.endress.com/cps71d](http://www.endress.com/cps71d)



Technical Information TI00245C

**Orbipore CPS91D**

- pH electrode with open aperture for media with high dirt load
- Product Configurator on the product page: [www.endress.com/cps91d](http://www.endress.com/cps91d)



Technical Information TI00375C

**Orbipac CPF81D**

- Compact pH sensor for installation or immersion operation
- In industrial water and wastewater
- Product Configurator on the product page: [www.endress.com/cpf81d](http://www.endress.com/cpf81d)



Technical Information TI00191C

**Pfautler electrodes****Ceramax CPS341D**

- pH electrode with pH-sensitive enamel
- Meets highest demands of measuring accuracy, pressure, temperature, sterility and durability
- Product Configurator on the product page: [www.endress.com/cps341d](http://www.endress.com/cps341d)



Technical Information TI00468C

**ORP sensors****Orbisint CPS12D**

- ORP sensor for process technology
- Product Configurator on the product page: [www.endress.com/cps12d](http://www.endress.com/cps12d)



Technical Information TI00367C

**Ceraliquid CPS42D**

- ORP electrode with ceramic junction and KCl liquid electrolyte
- Product Configurator on the product page: [www.endress.com/cps42d](http://www.endress.com/cps42d)



Technical Information TI00373C

#### **Ceragel CPS72D**

- ORP electrode with reference system including ion trap
- Product Configurator on the product page: [www.endress.com/cps72d](http://www.endress.com/cps72d)



Technical Information TI00374C

#### **Orbipac CPF82D**

- Compact ORP sensor for installation or immersion operation in process water and wastewater
- Product Configurator on the product page: [www.endress.com/cpf82d](http://www.endress.com/cpf82d)



Technical Information TI00191C

#### **Orbipore CPS92D**

- ORP electrode with open aperture for media with high dirt load
- Product Configurator on the product page: [www.endress.com/cps92d](http://www.endress.com/cps92d)



Technical Information TI00435C

#### **pH-ISFET sensors**

##### **Tophit CPS441D**

- Sterilizable ISFET sensor for low-conductivity media
- Liquid KCl electrolyte
- Product Configurator on the product page: [www.endress.com/cps441d](http://www.endress.com/cps441d)



Technical Information TI00352C

##### **Tophit CPS471D**

- Sterilizable and autoclavable ISFET sensor for food and pharmaceuticals, process engineering
- Water treatment and biotechnology
- Product Configurator on the product page: [www.endress.com/cps471d](http://www.endress.com/cps471d)



Technical Information TI00283C

##### **Tophit CPS491D**

- ISFET sensor with open aperture for media with high dirt load
- Product Configurator on the product page: [www.endress.com/cps491d](http://www.endress.com/cps491d)



Technical Information TI00377C

#### **Conductivity sensors with inductive measurement of conductivity**

##### **Indumax CLS50D**

- High-durability inductive conductivity sensor
- For standard and hazardous area applications
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cls50d](http://www.endress.com/cls50d)



Technical Information TI00182C

#### **Conductivity sensors with conductive measurement of conductivity**

##### **Condumax CLS15D**

- Conductive conductivity sensor
- For pure water, ultrapure water and hazardous area applications
- Product Configurator on the product page: [www.endress.com/CLS15d](http://www.endress.com/CLS15d)



Technical Information TI00109C

##### **Condumax CLS16D**

- Hygienic, conductive conductivity sensor
- For pure water, ultrapure water and Ex applications
- With EHEDG and 3A approval
- Product Configurator on the product page: [www.endress.com/CLS16d](http://www.endress.com/CLS16d)



Technical Information TI00227C

**Condumax CLS21D**

- Two-electrode sensor in plug-in head version version
- Product Configurator on the product page: [www.endress.com/CLS21d](http://www.endress.com/CLS21d)



Technical Information TI00085C

**Memosens CLS82D**

- Four-electrode sensor
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cls82d](http://www.endress.com/cls82d)



Technical Information TI01188C

**Oxygen sensors****Oxymax COS22D**

- Sterilizable sensor for dissolved oxygen
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cos22d](http://www.endress.com/cos22d)



Technical Information TI00446C

**Oxymax COS51D**

- Amperometric sensor for dissolved oxygen
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cos51d](http://www.endress.com/cos51d)



Technical Information TI00413C

**Oxymax COS61D**

- Optical oxygen sensor for drinking water and industrial water measurement
- Measuring principle: quenching
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cos61d](http://www.endress.com/cos61d)



Technical Information TI00387C

**Memosens COS81D**

- Sterilizable, optical sensor for dissolved oxygen
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cos81d](http://www.endress.com/cos81d)



Technical Information TI01201C

**Chlorine sensors****CCS142D**

- Membrane-covered amperometric sensor for free chlorine
- Measuring range 0.01 to 20 mg/l
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/ccs142d](http://www.endress.com/ccs142d)



Technical Information TI00419C

**Ion-selective sensors****ISEmax CAS40D**

- Ion selective sensors
- Product Configurator on the product page: [www.endress.com/cas40d](http://www.endress.com/cas40d)



Technical Information TI00491C

### **Turbidity sensors**

#### **Turbimax CUS51D**

- For nephelometric measurements of turbidity and solids in wastewater
- 4-beam scattered light method
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cus51d](http://www.endress.com/cus51d)



Technical Information TI00461C

#### **Turbimax CUS52D**

- Hygienic Memosens sensor for turbidity measurement in drinking water, process water and in utilities
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cus52d](http://www.endress.com/cus52d)



Technical Information TI01136C

### **SAC and nitrate sensors**

#### **Viomax CAS51D**

- SAC and nitrate measurement in drinking water and wastewater
- With Memosens technology
- Product Configurator on the product page: [www.endress.com/cas51d](http://www.endress.com/cas51d)



Technical Information TI00459C

### **Interface measurement**

#### **Turbimax CUS71D**

- Immersion sensor for interface measurement
- Ultrasonic interface sensor
- Product Configurator on the product page: [www.endress.com/cus71d](http://www.endress.com/cus71d)



Technical Information TI00490C

---





71588423

[www.addresses.endress.com](http://www.addresses.endress.com)

---