Safety Instructions Nivotester FTL325N

ATEX: II (1) G [Ex ia Ga] IIC

II (1) D [Ex ia Da] IIIC

IECEx: [Ex ia Ga] IIC

[Ex ia Da] IIIC







Nivotester FTL325N

Table of contents

About this document
Associated documentation
Supplementary documentation
Manufacturer's certificates
Manufacturer address 5
Other standards 5
Extended order code5
Safety instructions: General
Safety instructions: Installation
Temperature tables
Connection data

About this document



This document has been translated into several languages. Legally determined is solely the English source text.

The document translated into EU languages is available:

- In the download area of the Endress+Hauser website:
 www.endress.com -> Downloads -> Manuals and Datasheets ->
 Type: Ex Safety Instruction (XA) -> Text Search: ...
- In the Device Viewer: www.endress.com -> Product tools -> Access device specific information -> Check device features

Associated documentation

This document is an integral part of the following Operating Instructions:

BA01972F/00, BA01973F/00

Supplementary documentation

Explosion-protection brochure: CP00021Z/11

The Explosion-protection brochure is available:

- In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Media Type: Documentation -> Documentation Type: Brochures and catalogs -> Text Search: CP00021Z
- On the CD for devices with CD-based documentation

Manufacturer's certificates

EU Declaration of Conformity

Declaration Number:

EC 00528

The EU Declaration of Conformity is available:

In the download area of the Endress+Hauser website:

www.endress.com -> Downloads -> Declaration ->

Type: EU Declaration -> Product Code: ...

EU type-examination certificate

Certificate number:

DMT 01 ATEX E 052 X

List of applied standards: See EU Declaration of Conformity.

IEC Declaration of Conformity

Certificate number:

IECEx BVS 15,0085 X

Affixing the certificate number certifies conformity with the following standards (depending on the device version):

■ IEC 60079-0:2017 ■ IEC 60079-11:2011

Manufacturer address

Endress+Hauser SE+Co. KG Hauptstraße 1 79689 Maulburg, Germany Address of the manufacturing plant: See nameplate.

Other standards

Among other things, the following standards shall be observed in their current version for proper installation:

- IEC/EN 60079-14: "Explosive atmospheres Part 14: Electrical installations design, selection and erection"
- EN 1127-1: "Explosive atmospheres Explosion prevention and protection - Part 1: Basic concepts and methodology"

Extended order code

The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FTL325N	-	******	+	A*B*C*D*E*F*G*
(Device type)		(Basic		(Optional
		specifications)		specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available.

The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of

features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Nivotester



The following specifications reproduce an extract from the product structure and are used to assign:

- This documentation to the device (using the extended order code on the nameplate).
- The device options cited in the document.

Device type

FTL325N

Basic specifications

Position 1 (Approval)				
Selected option		Description		
FTL325N F		ATEX II (1) GD [Ex ia] IIC, WHG IECEX [Ex ia] IIC		
	Н	ATEX II (1) GD [Ex ia] IIC, WHG, SIL IECEX [Ex ia] IIC		

Position 2 (Housing)				
Selected option Description		Description		
FTL325N 1		Rail mounting, 22.5 mm, 1-channel		
	3	Rail mounting, 45 mm, 3-channel		

Position 3 (Power Supply)				
Selected option Description		Description		
FTL325N A		85-253 V AC		
E 20-30 V AC / 20-60 V DC		20-30 V AC / 20-60 V DC		

Position 4 (Switch Output)				
Selected option Description		Description		
FTL325N 1		1x SPDT level + 1x SPST alarm		
3		3x SPDT level + 1x SPST alarm		

Optional specifications


No options specific to hazardous locations are available.

Safety instructions: General

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- Comply with the installation and safety instructions in the Operating Instructions.
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Avoid electrostatic charging.

Safety instructions: Installation

One channel version




A0034562

₽ 1

- 1 Sensor, Limit level
- 2 Sensor
- 3 Level relay
- 4 Fault signal relay
- 5 Power supply

Three channel version



A0034563


₽ 2

CH1 Channel 1

CH2 Channel 2

CH3 Channel 3

- 1 Sensor, Limit level
- 2 Sensor
- 3 Level relay
- 4 Fault signal relay
- 5 Power supply



A0027418

№ 3

- A Min. 6 mm
- 1 Intrinsically safe contacts
- 2 Nivotester FTL325N
- *3 Other type, other product*
- To achieve an ingress protection of at least IP55: Protect the device from dust and humidity, e.g. in control rooms, or located in a suitable protective housing.
- The device is an associated apparatus: Only use the device outside explosion hazardous areas.
- If an intrinsically safe circuit is connected to the device passes through dust explosion-hazardous areas of Zones 20 or Zone 21, make sure that the devices connected to this circuit meet the requirements of categories 1 D or 2 D and are certified accordingly.
- There must be a distance (thread measure) of at least 50 mm between intrinsically safe and nonintrinsically safe terminals.
- When combining the device with other types and products on the same top-hat rail: Keep the distances comply to the relevant standards and rules.
- When combining with devices from other manufacturers: Observe ingress protection of the housing.

Intrinsic safety

- Observe the pertinent guidelines when interconnecting intrinsically safe circuits.
- The intrinsically-safe input circuits are galvanically isolated from other circuits up to a peak value of the nominal voltage of 375 V.

Temperature tables

Ambient temperature range	
Individual installation	$-20^{\circ}\text{C} \le T_a \le +60^{\circ}\text{C}$
Series installation	-20 °C ≤ T _a ≤ +50 °C

Connection data

Power supply circuit		
Terminal connections: 1, 2	AC voltage	$\begin{split} &U=85\text{ to }253\text{ V}_{AC}\text{, }50/60\text{ Hz}\\ &P\leq 1.75\text{ W (one channel version)}\\ &P\leq 2.75\text{ W (three channel version)} \end{split}$
	DC voltage	$\begin{split} &U = 20 \text{ to } 60 \text{ V}_{DC} \\ &U = 20 \text{ to } 30 \text{ V}_{AC}, 50/60 \text{ Hz} \\ &P \leq 1.20 \text{ W (one channel version)} \\ &P \leq 2.25 \text{ W (three channel version)} \end{split}$

Contact circuit					
Level relay Terminal connections: Channel 1 (CH1): 4, 5, 6 Channel 2 (CH2): 22, 23, 24 1) Channel 3 (CH3): 26, 27, 28 1)	$U \le 250~V_{AC},~I \le 2~A,~P \le 500~VA$ at $cos~\phi \ge 0.7$ $U \le 40~V_{DC},~I \le 2~A,~P \le 80~W$				
Fault signal relay Terminal connections: 15, 16					

1) not available in one channel version

Sensor circuit					
Terminal connections: Channel 1 (CH1): 7, 8 Channel 2 (CH2): 33, 34 ¹⁾ Channel 3 (CH3): 37, 38 ¹⁾	Connection data:	$\begin{array}{c} U_0 \leq 12 \ V \\ I_0 \leq 34 \ mA \\ P_0 \leq 154 \ mW \\ \\ Trapezium\text{-shaped cha} \\ \\ \hline \textbf{[Ex ia Ga] IIC} \end{array}$		$\begin{aligned} R_i &\geq 644 \; \Omega \\ C_i &= 0 \\ L_i &= 0 \\ \end{aligned}$ aracteristic	
				[Ex ia Ga] IIB [Ex ia Da] IIIC	
		Lo	Co	Lo	Co
	Max. external	0.5 mH	500 nF	1.0 mH	2.0 µF
	capacitance at max. external inductance	1.0 mH	450 nF	5.0 mH	1.5 µF
	Max. external capacitance or max. external inductance	30 mH	1.4 µF	120 mH	9.0 μF
If using explosion protection group		[Ex ib Gb] IIC		[Ex ib Gb] IIB	
[Ex ib Gb] IIC/IIB the application is limited to II (2) G		L _o	C _o	Lo	C _o
	Max. external capacitance or max. external inductance	30 mH	1.4 µF	120 mH	9.0 μF

¹⁾ not available in one channel version







www.addresses.endress.com