

Technical Information

Micropilot FMR63B

PROFIBUS PA

Free space radar



Level measurement in hygienic applications

Application

- Continuous, non-contact level measurement of liquids in hygienic applications
- Process connections: For hygiene applications (e.g.: Tri-Clamp or M24 adapter concept)
- Maximum measuring range: 80 m (262 ft)
- Temperature: -40 to +200 °C (-40 to +392 °F)
- Pressure: -1 to +25 bar (-14.5 to +363 psi)
- Accuracy: ±1 mm (±0.04 in)

Your benefits

- PTFE or PEEK antenna for hygienic requirements
- Reliable measurement thanks to strong signal focusing, even with multiple internal fixtures
- Easy, guided commissioning with intuitive user interface
- *Bluetooth*® wireless technology for commissioning, operation and maintenance
- Longer calibration cycles with Radar Accuracy Index

Table of contents

| | | | |
|------------------------------------------------------|-----------|-------------------------------------------------------------------------------|-----------|
| Important document information | 3 | Dielectric constant | 39 |
| Symbols | 3 | Mechanical construction | 39 |
| Graphic conventions | 4 | Dimensions | 39 |
| Function and system design | 4 | Weight | 49 |
| Measuring principle | 4 | Materials | 50 |
| Input | 5 | Display and user interface | 54 |
| Measured variable | 5 | Operation concept | 54 |
| Measuring range | 5 | Languages | 54 |
| Operating frequency | 12 | Local operation | 54 |
| Transmission power | 12 | Local display | 54 |
| Output | 12 | Remote operation | 56 |
| PROFIBUS PA | 12 | System integration | 56 |
| Signal on alarm | 12 | Supported operating tools | 57 |
| Linearization | 13 | Certificates and approvals | 57 |
| Protocol-specific data | 13 | CE mark | 57 |
| Power supply | 14 | RoHS | 57 |
| Terminal assignment | 14 | RCM marking | 57 |
| Terminals | 15 | Ex approvals | 57 |
| Available connectors | 15 | Pressure equipment with permitted pressure ≤ 200 bar (2 900 psi) | 57 |
| Supply voltage | 16 | Radio approval | 57 |
| Potential equalization | 16 | EN 302372 radio standard | 57 |
| Cable entries | 17 | FCC | 58 |
| Cable specification | 17 | Industry Canada | 58 |
| Overvoltage protection | 17 | External standards and guidelines | 58 |
| Performance characteristics | 18 | Ordering information | 58 |
| Reference operating conditions | 18 | Calibration | 59 |
| Maximum measured error | 18 | Service | 59 |
| Measured value resolution | 19 | Test, certificate, declaration | 60 |
| Response time | 19 | Identification | 60 |
| Influence of ambient temperature | 19 | Application packages | 60 |
| Influence of gas phase | 19 | Heartbeat Technology | 60 |
| Mounting | 20 | Accessories | 61 |
| Mounting location | 20 | Weather protection cover 316L | 61 |
| Orientation | 21 | Plastic weather protection cover | 62 |
| Installation instructions | 22 | Remote display FHX50B | 62 |
| Beam angle | 23 | Gas-tight feedthrough | 63 |
| Special mounting instructions | 24 | Process adapter M24 | 63 |
| Environment | 26 | Field Xpert SMT70 | 64 |
| Ambient temperature range | 26 | DeviceCare SFE100 | 64 |
| Ambient temperature limits | 26 | FieldCare SFE500 | 64 |
| Storage temperature | 36 | RID14 | 64 |
| Climate class | 36 | RID16 | 64 |
| Installation height as per IEC61010-1 Ed.3 | 36 | Fieldgate SFG500 | 65 |
| Degree of protection | 36 | Documentation | 65 |
| Vibration resistance | 37 | Document function | 66 |
| Electromagnetic compatibility (EMC) | 37 | Registered trademarks | 66 |
| Process | 37 | | |
| Process pressure range | 37 | | |

Important document information

Symbols

Safety symbols



This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.



This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in serious or fatal injury.



This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in minor or medium injury.



This symbol contains information on procedures and other facts which do not result in personal injury.

Electrical symbols



Direct current



Alternating current



Direct current and alternating current



Ground connection

A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.



Protective earth (PE)

Ground terminals that must be connected to ground prior to establishing any other connections. The ground terminals are located on the inside and outside of the device.

- Inner ground terminal; protective earth is connected to the mains supply.
- Outer ground terminal; device is connected to the plant grounding system.

Symbols for certain types of information and graphics



Permitted

Procedures, processes or actions that are permitted



Preferred

Procedures, processes or actions that are preferred



Forbidden

Procedures, processes or actions that are forbidden



Tip

Indicates additional information



Reference to documentation



Reference to graphic

1, 2, 3, ...

Item numbers

A, B, C, ...

Views



Hazardous area

Indicates the hazardous area



Safe area (non-hazardous area)

Indicates the non-hazardous area

Graphic conventions




- Installation, explosion and electrical connection drawings are presented in simplified format
- Devices, assemblies, components and dimensional drawings are presented in reduced-line format
- Dimensional drawings are not to-scale representations; the dimensions indicated are rounded off to 2 decimal places
- Unless otherwise described, flanges are presented with sealing surface form EN1091-1, B2; ASME B16.5, RF; JIS B2220, RF

Function and system design

Measuring principle

The Micropilot is a "downward-looking" measuring system, operating based on the frequency modulated continuous wave method (FMCW). The antenna emits an electromagnetic wave at a continuously varying frequency. This wave is reflected by the product and received again by the antenna.




A0032017

1 FMCW principle: transmission and reflection of the continuous wave

R Reference point of measurement

D Distance between reference point and product surface

The frequency of this wave is modulated in the form of a sawtooth signal between two limit frequencies f_1 and f_2 :



A0023771

2 FMCW principle: result of frequency modulation

1 Transmitted signal

2 Received signal

This results in the following difference frequency at any time between the transmitted signal and the received signal:

$$\Delta f = k \Delta t$$

where Δt is the run time and k is the specified increase in frequency modulation.

Δt is given by the distance D between the reference point R and the product surface:

$$D = (c \Delta t) / 2$$

where *c* is the speed of propagation of the wave.

In summary, *D* can be calculated from the measured difference frequency Δf . *D* is then used to determine the content of the tank or silo.

Input

| | |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Measured variable | The measured variable is the distance between the reference point and the product surface. The level is calculated based on "E", the empty distance entered. |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Measuring range | The measuring range starts at the point where the beam hits the tank floor. Levels below this point cannot be measured, particularly in the case of spherical bases or conical outlets. |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Maximum measuring range

The maximum measuring range depends on the antenna size and design.


| Antenna | Maximum measuring range |
|-----------------------------------------|-------------------------|
| Integrated, PEEK, 20 mm (0.75 in) | 10 m (32.8 ft) |
| Cladded flush mount, PTFE, 50 mm (2 in) | 50 m (164 ft) |
| Cladded flush mount, PTFE, 80 mm (3 in) | 80 m (262 ft) |

Usable measuring range

The usable measuring range depends on the antenna size, the medium's reflective properties, the installation position and any possible interference reflections.

In principle, measurement is possible up to the tip of the antenna.

To avoid any material damage from corrosive or aggressive media or deposit buildup on the antenna, the end of the measuring range should be selected 10 mm (0.4 in) before the tip of the antenna.



A0051658

3 Usable measuring range

- A Length of antenna + 10 mm (0.4 in)
- B Usable measuring range
- C 50 to 80 mm (1.97 to 3.15 in); medium $\epsilon_r < 2$
- H Vessel height
- R Reference point of measurement, varies depending on the antenna system

For further information on the reference point, see → Mechanical construction.

In the case of media with a low dielectric constant, $\epsilon_r < 2$, the tank floor may be visible through the medium at very low levels (lower than level C). Reduced accuracy must be expected in this range. If this is not acceptable, the zero point should be positioned at a distance C above the tank floor in these applications → Usable measuring range.

The media groups and the possible measuring range are described as a function of the application and media group in the following section. If the dielectric constant of the medium is not known, to ensure a reliable measurement assume the medium belongs to group B.

Media groups

- **A0** (ϵ_r 1.2 to 1.4)
e.g. n-butane, liquid nitrogen, liquid hydrogen
- **A** (ϵ_r 1.4 to 1.9)
Non-conductive liquids, e.g. liquefied gas
- **B** (ϵ_r 1.9 to 4)
Non-conductive liquids, e.g. gasoline, oil, toluene, etc.
- **C** (ϵ_r 4 to 10)
e.g. concentrated acid, organic solvents, ester, aniline, etc.
- **D** ($\epsilon_r > 10$)
Conductive liquids, aqueous solutions, diluted acids, bases and alcohol

i Measurement of the following media with absorbing gas phase

For example:

- Ammonia
- Acetone
- Methylene chloride
- Methyl ethyl ketone
- Propylene oxide
- VCM (vinyl chloride monomer)

To measure absorbing gases, either use a guided radar, measuring devices with another measuring frequency or another measuring principle.

If measurements must be performed in one of these media, please contact Endress+Hauser.


i For the dielectric constants (DC values) of many media commonly used in industry, please refer to:

- Dielectric constant (DC value) Compendium CP01076F
- The Endress+Hauser "DC Values app" (available for Android and iOS)


*Measurement in storage vessel***Storage vessel - measuring conditions**

Calm medium surface (e.g. bottom filling, filling via immersion tube or rare filling from above)


Integrated antenna, PEEK, 20 mm (0.75 in) in storage vessel

| | Media group | Measuring range |
|-------------------------------------------------------------------------------------|--------------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 1.5 m (5 ft) |
| | A (ϵ_r 1.4 to 1.9) | 2.5 m (8 ft) |
| | B (ϵ_r 1.9 to 4) | 5 m (16 ft) |
| | C (ϵ_r 4 to 10) | 8 m (26 ft) |
| | D ($\epsilon_r > 10$) | 10 m (33 ft) |


Antenna, PTFE cladded flush mount, 50 mm (2 in) in storage vessel

| | Media group | Measuring range |
|-----------------------------------------------------------------------------------|--------------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 7 m (23 ft) |
| | A (ϵ_r 1.4 to 1.9) | 12 m (39 ft) |
| | B (ϵ_r 1.9 to 4) | 23 m (75 ft) |
| | C (ϵ_r 4 to 10) | 40 m (131 ft) |
| | D (ϵ_r >10) | 50 m (164 ft) |


Antenna, PTFE cladded flush mount, 80 mm (3 in) in storage vessel

| | Media group | Measuring range |
|------------------------------------------------------------------------------------|--------------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 22 m (72 ft) |
| | A (ϵ_r 1.4 to 1.9) | 40 m (131 ft) |
| | B (ϵ_r 1.9 to 4) | 50 m (164 ft) |
| | C (ϵ_r 4 to 10) | 65 m (231 ft) |
| | D (ϵ_r >10) | 80 m (262 ft) |

Cladded antenna, PEEK, 20 mm (0.75 in) in storage vessel

| | Media group | Measuring range |
|-------------------------------------------------------------------------------------|--------------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 1.5 m (5 ft) |
| | A (ϵ_r 1.4 to 1.9) | 2.5 m (8 ft) |
| | B (ϵ_r 1.9 to 4) | 5 m (16 ft) |
| | C (ϵ_r 4 to 10) | 8 m (26 ft) |
| | D (ϵ_r >10) | 10 m (33 ft) |


Cladded antenna, PEEK, 40 mm (1.5 in) in storage vessel

| | Media group | Measuring range |
|-----------------------------------------------------------------------------------|-------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 3 m (10 ft) |
| | A (ϵ_r 1.4 to 1.9) | 6 m (20 ft) |
| | B (ϵ_r 1.9 to 4) | 11 m (36 ft) |
| | C (ϵ_r 4 to 10) | 15 m (49 ft) |
| | D ($\epsilon_r > 10$) | 22 m (72 ft) |


*Measurement in buffer vessel***Buffer vessel - measuring conditions**

Moving medium surface (e.g. permanent free filling from above, mixing jets)


Integrated antenna, PEEK, 20 mm (0.75 in) in buffer vessel

| | Media group | Measuring range |
|------------------------------------------------------------------------------------|-------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 1 m (3.3 ft) |
| | A (ϵ_r 1.4 to 1.9) | 1.5 m (5 ft) |
| | B (ϵ_r 1.9 to 4) | 3 m (10 ft) |
| | C (ϵ_r 4 to 10) | 6 m (20 ft) |
| | D ($\epsilon_r > 10$) | 8 m (26 ft) |


Antenna, PTFE cladded flush mount, 50 mm (2 in) in buffer vessel

| | Media group | Measuring range |
|-------------------------------------------------------------------------------------|-------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 4 m (13 ft) |
| | A (ϵ_r 1.4 to 1.9) | 7 m (23 ft) |
| | B (ϵ_r 1.9 to 4) | 13 m (43 ft) |
| | C (ϵ_r 4 to 10) | 28 m (92 ft) |
| | D ($\epsilon_r > 10$) | 44 m (144 ft) |


Antenna, PTFE cladded flush mount, 80 mm (3 in) in buffer vessel

| | Media group | Measuring range |
|-----------------------------------------------------------------------------------|-------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 12 m (39 ft) |
| | A (ϵ_r 1.4 to 1.9) | 23 m (75 ft) |
| | B (ϵ_r 1.9 to 4) | 45 m (148 ft) |
| | C (ϵ_r 4 to 10) | 60 m (197 ft) |
| | D (ϵ_r >10) | 70 m (230 ft) |

Cladded antenna, PEEK, 20 mm (0.75 in) in buffer vessel

| | Media group | Measuring range |
|------------------------------------------------------------------------------------|-------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 1 m (3.3 ft) |
| | A (ϵ_r 1.4 to 1.9) | 1.5 m (5 ft) |
| | B (ϵ_r 1.9 to 4) | 3 m (10 ft) |
| | C (ϵ_r 4 to 10) | 6 m (20 ft) |
| | D (ϵ_r >10) | 8 m (26 ft) |


Cladded antenna, PEEK, 40 mm (1.5 in) in buffer vessel

| | Media group | Measuring range |
|-------------------------------------------------------------------------------------|-------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 1.5 m (5 ft) |
| | A (ϵ_r 1.4 to 1.9) | 3 m (10 ft) |
| | B (ϵ_r 1.9 to 4) | 6 m (20 ft) |
| | C (ϵ_r 4 to 10) | 13 m (43 ft) |
| | D (ϵ_r >10) | 20 m (66 ft) |


*Measurement in vessel with agitator***Vessel with agitator - measuring conditions**

Turbulent medium surface (e.g. from filling from above, stirrers and baffles)


Integrated antenna, PEEK, 20 mm (0.75 in) in vessel with agitator

| | Media group | Measuring range |
|-----------------------------------------------------------------------------------|-------------------------------------|-----------------|
|  | A (ϵ_r 1.4 to 1.9) | 1 m (3.3 ft) |
| | B (ϵ_r 1.9 to 4) | 1.5 m (5 ft) |
| | C (ϵ_r 4 to 10) | 3 m (10 ft) |
| | D (ϵ_r >10) | 5 m (16 ft) |


Antenna, PTFE clad flush mount, 50 mm (2 in) in vessel with agitator

| | Media group | Measuring range |
|------------------------------------------------------------------------------------|--------------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 2 m (7 ft) |
| | A (ϵ_r 1.4 to 1.9) | 4 m (13 ft) |
| | B (ϵ_r 1.9 to 4) | 7 m (23 ft) |
| | C (ϵ_r 4 to 10) | 15 m (49 ft) |
| | D (ϵ_r >10) | 25 m (82 ft) |


Antenna, PTFE clad flush mount, 80 mm (3 in) in vessel with agitator

| | Media group | Measuring range |
|-------------------------------------------------------------------------------------|--------------------------------------|-----------------|
|  | A0 (ϵ_r 1.2 to 1.4) | 7 m (23 ft) |
| | A (ϵ_r 1.4 to 1.9) | 13 m (43 ft) |
| | B (ϵ_r 1.9 to 4) | 25 m (82 ft) |
| | C (ϵ_r 4 to 10) | 50 m (164 ft) |
| | D (ϵ_r >10) | 60 m (197 ft) |

Cladded antenna, PEEK, 20 mm (0.75 in) in vessel with agitator

|  | Media group | Measuring range |
|-----------------------------------------------------------------------------------|------------------------------|-----------------|
| | A (ϵ_r 1.4 to 1.9) | 1 m (3.3 ft) |
| | B (ϵ_r 1.9 to 4) | 1.5 m (5 ft) |
| | C (ϵ_r 4 to 10) | 3 m (10 ft) |
| | D ($\epsilon_r > 10$) | 5 m (16 ft) |

Cladded antenna, PEEK, 40 mm (1.5 in) in vessel with agitator

|  | Media group | Measuring range |
|------------------------------------------------------------------------------------|-------------------------------|-----------------|
| | A0 (ϵ_r 1.2 to 1.4) | 1 m (3.3 ft) |
| | A (ϵ_r 1.4 to 1.9) | 1.5 m (5 ft) |
| | B (ϵ_r 1.9 to 4) | 3 m (10 ft) |
| | C (ϵ_r 4 to 10) | 7 m (23 ft) |
| | D ($\epsilon_r > 10$) | 11 m (36 ft) |

| | |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Operating frequency | Approx. 80 GHz Up to 8 devices can be installed in a tank without the devices mutually influencing one another. |
| Transmission power | <ul style="list-style-type: none"> Peak power: <1.5 mW Average output power: <70 μW |

Output

| | |
|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| PROFIBUS PA | <p>According to EN 50170 Volume 2, IEC 61158-2</p> <p>Signal coding: Manchester Bus Powered (MBP) type 1</p> <p>Data transmission rate: 31.25 kBit/s, voltage mode</p> <p>Galvanic isolation: Yes</p> |
| Signal on alarm | <p>Diagnostics in accordance with PROFIBUS PA Profile 3.02</p> <p>Local display Status signal (in accordance with NAMUR Recommendation NE 107): Plain text display</p> |

Operating tool via service interface (CDI)

Status signal (in accordance with NAMUR Recommendation NE 107):

Plain text display

Operating tool via PROFIBUS PA communication

Status signal (in accordance with NAMUR Recommendation NE 107):

Plain text display

Linearization

The linearization function of the device allows the conversion of the measured value into any unit of length, weight, flow or volume.

Pre-programmed linearization curves

Linearization tables for calculating the volume in the following vessels are preprogrammed into the device:

- Pyramid bottom
- Conical bottom
- Angled bottom
- Horizontal cylinder
- Sphere

Other linearization tables of up to 32 value pairs can be entered manually.

Protocol-specific data**PROFIBUS PA****Manufacturer ID:**

17 (0x11)

Ident number:

0x1568 or 0x9700

Profile version:

3.02

GSD file and version


Information and files available at:

- www.endress.com
On the product page for the device: Documents/Software → Device drivers
- www.profibus.com

*Output values***Analog Input:**

- Level linearized
- Distance
- Volume
- Terminal voltage
- Electronic temperature
- Sensor temperature
- Absolute echo amplitude
- Relative echo amplitude
- Area of incoupling
- Build-up index, optional (Guidance → Heartbeat Technology → Build-up detection → Build-up index)
- Foam index, optional (Diagnostics → Heartbeat Technology → Foam detection → Foam index)

Digital Input:

-  Is only available if the "Heartbeat Verification + Monitoring" application package was selected.
- 168 Build-up detected, optional (Guidance → Heartbeat Technology → Build-up detection → 168 Build-up detected)
- 952 Foam detected, optional (Guidance → Heartbeat Technology → Foam detection → 952 Foam detected)

*Input values***Analog Output:**

Analog value from PLC to be indicated on the display


Supported functions

- Identification & maintenance
Straightforward device identification on the part of the control system and nameplate
- Automatic Ident Number adoption
GSD compatibility mode for generic profile 0x9700 "Transmitter with 1 Analog Input"
- Physical layer diagnostics
Installation check of the PROFIBUS segment and device using terminal voltage and message monitoring
- PROFIBUS upload/download
Reading and writing parameters is up to ten times faster with PROFIBUS upload/download
- Condensed status
Straightforward and self-explanatory diagnostic information by categorizing diagnostic messages that occur

Power supply

Terminal assignment

Single compartment housing




A0042594


4 Connection terminals and ground terminal in the connection compartment

- 1 Positive terminal
- 2 Negative terminal
- 3 Internal ground terminal

Dual compartment housing




A0042803


 5 Connection terminals and ground terminal in the connection compartment

- 1 Positive terminal
- 2 Negative terminal
- 3 Internal ground terminal

Dual compartment housing, L-form



A0045842


 6 Connection terminals and ground terminal in the connection compartment

- 1 Positive terminal
- 2 Negative terminal
- 3 Internal ground terminal

Terminals


- Supply voltage and internal ground terminal: 0.5 to 2.5 mm² (20 to 14 AWG)
- External ground terminal: 0.5 to 4 mm² (20 to 12 AWG)

Available connectors


-  In the case of devices with a plug, it is not necessary to open the housing for connection purposes.

Use the enclosed seals to prevent the penetration of moisture into the device.

Devices with M12 plug



A0011175

 7 View of the plug-in connection on the device

- 1 Signal +
- 2 Not assigned
- 3 Signal -
- 4 Ground

Various M12 sockets are available as accessories for devices with M12 plugs.

Supply voltage

The supply voltage depends on the selected type of device approval

| | |
|-------------------------------------------------------------|-------------------------|
| Non-hazardous, Ex d, Ex e | 9 to 32 V _{DC} |
| Ex i | 9 to 30 V _{DC} |
| Nominal current | 14 mA |
| Failure current FDE (Fault Disconnection Electronic) | 0 mA |




- Use only suitable and certified Profibus PA components (e.g. DP/PA segment coupler) for the power supply
- FISCO/FNICO-compliant according to IEC 60079-27
- The supply is not polarity-dependent

Device display and Bluetooth

The display background lighting and Bluetooth function (order option) is guaranteed across the entire supply voltage range. The Bluetooth function can be restricted at high ambient temperatures.

Potential equalization

The protective ground on the device must not be connected. If necessary, the potential matching line can be connected to the outer ground terminal of the transmitter before the device is connected.



A0046583

- A Single compartment housing, plastic
- B Single compartment housing, aluminum
- C Single compartment housing, 316L hygiene (Ex device)
- D Dual compartment housing
- E Dual compartment housing, L-form
- 1 Ground terminal for connecting the potential matching line


⚠ WARNING**Explosion Hazard!**

- Please refer to the separate documentation on applications in hazardous areas for the safety instructions.



For optimum electromagnetic compatibility:

- Keep the potential matching line as short as possible
- Observe a cross-section of at least 2.5 mm² (14 AWG)

Cable entries

A0046584

- A Single compartment housing, plastic
 B Single compartment housing, aluminum
 C Single compartment housing, 316L hygiene
 D Dual compartment housing
 E Dual compartment housing, L-form
 1 Cable entry
 2 Dummy plug

The type of cable entry depends on the device version ordered.



Always route connecting cables downwards so that moisture cannot penetrate the connection compartment.

If necessary, create a drip loop or use a weather protection cover.

Cable specification**Rated cross-section**

- Supply voltage
0.5 to 2.5 mm² (20 to 13 AWG)
- Protective earth or grounding of the cable shield
> 1 mm² (17 AWG)
- External ground terminal
0.5 to 4 mm² (20 to 12 AWG)

Cable outer diameter

The cable outer diameter depends on the cable gland used

- Coupling, plastic:
ø5 to 10 mm (0.2 to 0.38 in)
- Coupling, nickel-plated brass:
ø7 to 10.5 mm (0.28 to 0.41 in)
- Coupling, stainless steel:
ø7 to 12 mm (0.28 to 0.47 in)



Use a twisted, shielded twin-core cable, preferably cable type A.

For further information on the cable specification:

- Operating Instructions BA00034S "PROFIBUS DP/PA: Guidelines for planning and commissioning"
- PROFIBUS Assembling Guideline 8.022
- IEC 61158-2 (MBP).

Overvoltage protection

The overvoltage protection can optionally be ordered as a "Mounted accessory" via the product structure

Devices without optional overvoltage protection

The equipment fulfills the requirements of the product standard IEC / DIN EN 61326-1 (Table 2 Industrial Environment).

Depending on the type of port (DC power supply, input/output port) different testing levels according to IEC / DIN EN 61326-1 against transient overvoltages (Surge) are applied (IEC / DIN EN 61000-4-5 Surge):

Test level on DC power ports and input/output ports is 1 000 V line to earth

Devices with optional overvoltage protection

- Spark-over voltage: min. 400 V_{DC}
- Tested according to IEC / DIN EN 60079-14 sub chapter 12.3 (IEC / DIN EN 60060-1 chapter 7)
- Nominal discharge current: 10 kA

NOTICE

Device could be destroyed

- ▶ Always ground device with integrated overvoltage protection.

Overvoltage category

Overvoltage category II

Performance characteristics

Reference operating conditions

- Temperature = +24 °C (+75 °F) ±5 °C (±9 °F)
- Pressure = 960 mbar abs. (14 psia) ±100 mbar (±1.45 psi)
- Humidity = 60 % ±15 %
- Reflector: metal plate with diameter ≥ 1 m (40 in)
- No major interference reflections inside the signal beam

Maximum measured error

Reference accuracy

Accuracy

The accuracy is the sum of the non-linearity, non-repeatability and hysteresis.

- Measuring distance up to 0.8 m (2.62 ft): max. ±4 mm (±0.16 in)
- Measuring distance > 0.8 m (2.62 ft): ±1 mm (±0.04 in)


Non-repeatability

Non-repeatability is already included in the accuracy.
≤ 1 mm (0.04 in)



If conditions deviate from the reference operating conditions, the offset/zero point that results from the installation conditions can be up to ±4 mm (±0.16 in). This additional offset/zero point can be eliminated by entering a correction (**Level correction** parameter) during commissioning.

Differing values in near-range applications



A0032636

8 Maximum measured error in near-range applications

Δ Maximum measured error

R Reference point of the distance measurement

D Distance from reference point of antenna

Measured value resolution

Dead band according to DIN EN IEC 61298-2/DIN EN IEC 60770-1:

Digital: 1 mm

Response time

According to DIN EN IEC 61298-2 / DIN EN IEC 60770-1, the step response time is the time following an abrupt change in the input signal up until the changed output signal has adopted 90 % of the steady-state value for the first time.

The response time can be configured.

The following step response times apply (in accordance with DIN EN IEC 61298-2/DIN EN IEC 60770-1) when damping is switched off:

- Pulse frequency $\geq 5/s$ (cycle time ≤ 200 ms)
- Step response time < 1 s

Influence of ambient temperature

The output changes due to the effect of the ambient temperature with respect to the reference temperature.

The measurements are performed according to DIN EN IEC 61298-3/DIN EN IEC 60770-1

Average $T_C = 2$ mm/10 K

Influence of gas phase

High pressure reduces the speed of propagation of the measuring signals in the gas/vapor above the medium. This effect depends on the type of gas phase and its temperature. This results in a systematic measured error that increases with increasing distance between the reference point of the measurement (flange) and the surface of the product. The following table shows this measured error for some typical gases/vapors (with regard to the distance, a positive value means that an excessively large distance is measured):

Measured error for some typical gases/vapors


| Gas phase | Temperature | Pressure | | |
|--------------|-------------------|------------------|------------------|------------------|
| | | 1 bar (14.5 psi) | 10 bar (145 psi) | 25 bar (362 psi) |
| Air/nitrogen | +20 °C (+68 °F) | 0.00 % | +0.22 % | +0.58 % |
| | +200 °C (+392 °F) | -0.01 % | +0.13 % | +0.36 % |
| | +400 °C (+752 °F) | -0.02 % | +0.08 % | +0.29 % |
| Hydrogen | +20 °C (+68 °F) | -0.01 % | +0.10 % | +0.25 % |
| | +200 °C (+392 °F) | -0.02 % | +0.05 % | +0.17 % |

| Gas phase | Temperature | Pressure | | |
|-------------------------|-------------------|------------------|------------------|------------------|
| | | 1 bar (14.5 psi) | 10 bar (145 psi) | 25 bar (362 psi) |
| | +400 °C (+752 °F) | -0.02 % | +0.03 % | +0.11 % |
| Water (saturated steam) | +100 °C (+212 °F) | +0.02 % | - | - |
| | +180 °C (+356 °F) | - | +2.10 % | - |
| | +263 °C (+505 °F) | - | - | +4.15 % |
| | +310 °C (+590 °F) | - | - | - |
| | +364 °C (+687 °F) | - | - | - |

i With a known, constant pressure, it is possible to compensate for this measured error with a linearization, for example.


Mounting

Mounting location




A0016882

- A Recommended distance from wall to nozzle outer edge ~ 1/6 of the vessel diameter. The device should never be mounted closer than 15 cm (5.91 in) to the tank wall.
- 1 Use of a weather protection cover; protection from direct sunlight or rain
- 2 Installation in the center, interference can cause signal loss
- 3 Do not install above the filling curtain

Orientation**Internal vessel fittings**

A0031777

Avoid internal fittings (point level switches, temperature sensors, struts, vacuum rings, heating coils, baffles etc.) inside the signal beam. Pay attention to the beam angle α .

Avoiding interference echoes

A0031813

Metal deflector plates, installed at an angle to scatter the radar signals, help prevent interference echoes.

Vertical alignment of antenna axis

Align the antenna so that it is perpendicular to the product surface.



The maximum reach of the antenna can be reduced, or additional interference signals can occur, if the antenna is not installed perpendicular to the product.


Radial alignment of the antenna

Based on the directional characteristic, radial alignment of the antenna is not necessary.

Installation instructions**Integrated antenna, PEEK 20 mm (0.75 in)***Information about the mounting nozzle*

The maximum nozzle length H_{max} depends on the nozzle diameter D .

Maximum nozzle length H_{max} as a function of the nozzle diameter D

|  | ϕD | H_{max} |
|-----------------------------------------------------------------------------------|----------------------------|----------------|
| | 40 to 50 mm (1.6 to 2 in) | 200 mm (8 in) |
| | 50 to 80 mm (2 to 3.2 in) | 300 mm (12 in) |
| | 80 to 100 mm (3.2 to 4 in) | 450 mm (18 in) |
| | 100 to 150 mm (4 to 6 in) | 550 mm (22 in) |
| | ≥ 150 mm (6 in) | 850 mm (34 in) |



In the case of longer nozzles, reduced measuring performance must be expected.


Please note the following:

- The end of the nozzle must be smooth and free from burrs.
- The edge of the nozzle should be rounded.
- Mapping must be performed.
- Please contact the manufacturer's support department for applications with nozzles that are higher than indicated in the table.

Antenna, PTFE clad, flush mount 50 mm (2 in)*Information about the mounting nozzle*

The maximum nozzle length H_{max} depends on the nozzle diameter D .

The maximum length of the nozzle H_{max} depends on the nozzle diameter D

|  | ϕD | H_{max} |
|-------------------------------------------------------------------------------------|----------------------------|------------------|
| | 50 to 80 mm (2 to 3.2 in) | 600 mm (24 in) |
| | 80 to 100 mm (3.2 to 4 in) | 1 000 mm (40 in) |
| | 100 to 150 mm (4 to 6 in) | 1 250 mm (50 in) |
| | ≥ 150 mm (6 in) | 1 850 mm (74 in) |



In the case of longer nozzles, reduced measuring performance must be expected.


Please note the following:


- The end of the nozzle must be smooth and free from burrs.
- The edge of the nozzle should be rounded.
- Mapping must be performed.
- Please contact the manufacturer's support department for applications with nozzles that are higher than indicated in the table.

Antenna, PTFE clad, flush mount 80 mm (3 in)*Information about the mounting nozzle*

The maximum nozzle length H_{max} depends on the nozzle diameter D .

The maximum length of the nozzle H_{max} depends on the nozzle diameter D

|  | ϕD | H_{max} |
|-----------------------------------------------------------------------------------|----------------------------|-------------------|
| | 80 to 100 mm (3.2 to 4 in) | 1 750 mm (70 in) |
| | 100 to 150 mm (4 to 6 in) | 2 200 mm (88 in) |
| | ≥ 150 mm (6 in) | 3 300 mm (132 in) |


 In the case of longer nozzles, reduced measuring performance must be expected.

Please note the following:


- The end of the nozzle must be smooth and free from burrs.
- The edge of the nozzle should be rounded.
- Mapping must be performed.
- Please contact the manufacturer's support department for applications with nozzles that are higher than indicated in the table.


Beam angle

The beam angle is defined as the angle α where the energy density of the radar waves reaches half the value of the maximum energy density (3 dB width). Microwaves are also emitted outside the signal beam and can be reflected off interfering installations.




A0031824


 9 Relationship between beam angle α , distance D and beamwidth diameter W

 The beamwidth diameter W depends on the beam angle α and the distance D .


Integrated antenna, PEEK 20 mm / 3/4", α 14 °

| $W = D \times 0.26$ | D | W |
|-------------------------------------------------------------------------------------|--------------|------------------|
|  | 5 m (16 ft) | 1.23 m (4.04 ft) |
| | 10 m (33 ft) | 2.46 m (8.07 ft) |

PTFE cladded, flush mount 50 mm (2 in) antenna, α 7 °


| $W = D \times 0.12$ | D | W |
|-----------------------------------------------------------------------------------|---------------|-------------------|
|  | 5 m (16 ft) | 0.61 m (2.00 ft) |
| | 10 m (33 ft) | 1.22 m (4.00 ft) |
| | 15 m (49 ft) | 1.83 m (6.00 ft) |
| | 20 m (66 ft) | 2.44 m (8.01 ft) |
| | 25 m (82 ft) | 3.05 m (10.01 ft) |
| | 30 m (98 ft) | 3.66 m (12.01 ft) |
| | 35 m (115 ft) | 4.27 m (14.01 ft) |
| | 40 m (131 ft) | 4.88 m (16.01 ft) |
| | 45 m (148 ft) | 5.50 m (18.04 ft) |
| | 50 m (164 ft) | 6.11 m (20.05 ft) |

PTFE cladded, flush mount 80 mm (3 in) antenna, α 3 °

| $W = D \times 0.05$ | D | W |
|------------------------------------------------------------------------------------|---------------|-------------------|
|  | 5 m (16 ft) | 0.25 m (0.82 ft) |
| | 10 m (33 ft) | 0.50 m (1.64 ft) |
| | 15 m (49 ft) | 0.75 m (2.46 ft) |
| | 20 m (66 ft) | 1.00 m (3.28 ft) |
| | 25 m (82 ft) | 1.25 m (4.10 ft) |
| | 30 m (98 ft) | 1.50 m (4.92 ft) |
| | 35 m (115 ft) | 1.75 m (5.74 ft) |
| | 40 m (131 ft) | 2.00 m (6.56 ft) |
| | 45 m (148 ft) | 2.25 m (7.38 ft) |
| | 50 m (164 ft) | 2.50 m (8.20 ft) |
| | 60 m (197 ft) | 3.00 m (9.84 ft) |
| | 70 m (230 ft) | 3.50 m (11.48 ft) |
| | 80 m (262 ft) | 4.00 m (13.12 ft) |

Special mounting instructions

Measurement through a ball valve



A0034564

- Measurements can be performed through an open full bore ball valve without any problems.
- At the transitions, no gap exceeding 1 mm (0.04 in) may be left.
- Opening diameter of ball valve must always correspond to the pipe diameter; avoid edges and constrictions.

External measurement through plastic cover or dielectric windows

- Dielectric constant of medium: $\epsilon_r \geq 10$
- The distance from the tip of the antenna to the tank should be approx. 100 mm (4 in).
- Avoid installation positions where condensate or buildup can form between the antenna and the vessel
- In the case of outdoor installations, ensure that the area between the antenna and the tank is protected from the weather
- Do not install any fittings or attachments between the antenna and the tank that could reflect the signal


The thickness of the tank ceiling or the dielectric window depends on the ϵ_r of the material.

The material thickness can be a full multiple of the optimum thickness (table); it is important to note, however, that the microwave transparency decreases significantly with increasing material thickness.

Optimum material thickness

| Material | Optimum material thickness |
|---------------------------|----------------------------|
| PE; ϵ_r 2.3 | 1.25 mm (0.049 in) |
| PTFE; ϵ_r 2.1 | 1.30 mm (0.051 in) |
| PP; ϵ_r 2.3 | 1.25 mm (0.049 in) |
| Perspex; ϵ_r 3.1 | 1.10 mm (0.043 in) |

Container with heat insulation



A0046566

If process temperatures are high, the device should be included in the usual container insulation system (2) to prevent the electronics from heating as a result of thermal radiation or convection. The rib structure (1) must not be insulated.

Environment

Ambient temperature range

The following values apply up to a process temperature of +85 °C (+185 °F). At higher process temperatures, the permitted ambient temperature is reduced.

- Without LCD display:
Standard: -40 to +85 °C (-40 to +185 °F)
- With LCD display: -40 to +85 °C (-40 to +185 °F) with limitations in optical properties such as display speed and contrast for example. Can be used without limitations up to -20 to +60 °C (-4 to +140 °F)



If operating outdoors in strong sunlight:

- Mount the device in the shade.
- Avoid direct sunlight, particularly in warm climatic regions.
- Use a weather protection cover (see accessories).

Ambient temperature limits

The permitted ambient temperature (T_a) depends on the selected housing material (Product Configurator → Housing; Material →) and the selected process temperature range (Product Configurator → Application →).


In the event of temperature (T_p) at the process connection, the permitted ambient temperature (T_a) is reduced.



The following information only takes functional aspects into consideration. Additional restrictions may apply for certified device versions.

Plastic housing

Plastic housing; process temperature -10 to +150 °C (+14 to +302 °F)



A0032024


10 Plastic housing; process temperature -10 to +150 °C (+14 to +302 °F)

| | | | | | | |
|----|---|---------|-------------------|--|---------|------------------|
| P1 | = | T_p : | -10 °C (+14 °F) | | T_a : | +76 °C (+169 °F) |
| P2 | = | T_p : | +76 °C (+169 °F) | | T_a : | +76 °C (+169 °F) |
| P3 | = | T_p : | +150 °C (+302 °F) | | T_a : | +25 °C (+77 °F) |
| P4 | = | T_p : | +150 °C (+302 °F) | | T_a : | -10 °C (+14 °F) |
| P5 | = | T_p : | -10 °C (+14 °F) | | T_a : | -10 °C (+14 °F) |



The selected process temperature range is restricted from -10 to +150 °C (+14 to +302 °F) to 0 to +150 °C (+32 to +302 °F) in devices with a plastic housing and CSA C/US approval.

Process temperature restricted to 0 to +150 °C (+32 to +302 °F) for CSA C/US approval and plastic housing




A0048826

11 Plastic housing; process temperature 0 to +150 °C (+32 to +302 °F) for CSA C/US approval

| | | | | |
|----|---|---------------------------|--|--------------------------|
| P1 | = | T_p : 0 °C (+32 °F) | | T_a : +76 °C (+169 °F) |
| P2 | = | T_p : +76 °C (+169 °F) | | T_a : +76 °C (+169 °F) |
| P3 | = | T_p : +150 °C (+302 °F) | | T_a : +25 °C (+77 °F) |
| P4 | = | T_p : +150 °C (+302 °F) | | T_a : 0 °C (+32 °F) |
| P5 | = | T_p : 0 °C (+32 °F) | | T_a : 0 °C (+32 °F) |

Plastic housing; process temperature -10 to +200 °C (+14 to +392 °F)



A0032024


12 Plastic housing; process temperature -10 to +200 °C (+14 to +392 °F)

| | | | | |
|----|---|---------------------------|--|--------------------------|
| P1 | = | T_p : -10 °C (+14 °F) | | T_a : +76 °C (+169 °F) |
| P2 | = | T_p : +76 °C (+169 °F) | | T_a : +76 °C (+169 °F) |
| P3 | = | T_p : +200 °C (+392 °F) | | T_a : +27 °C (+81 °F) |
| P4 | = | T_p : +200 °C (+392 °F) | | T_a : -10 °C (+14 °F) |
| P5 | = | T_p : -10 °C (+14 °F) | | T_a : -10 °C (+14 °F) |



The selected process temperature range is restricted from -10 to +200 °C (+14 to +392 °F) to 0 to +200 °C (+32 to +392 °F) in devices with a plastic housing and CSA C/US approval.

Process temperature restricted to 0 to +200 °C (+32 to +392 °F) for CSA C/US approval and plastic housing




A0048826

13 Plastic housing; process temperature 0 to +200 °C (+32 to +392 °F) for CSA C/US approval

| | | | | |
|----|---|---------------------------|--|--------------------------|
| P1 | = | T_p : 0 °C (+32 °F) | | T_a : +76 °C (+169 °F) |
| P2 | = | T_p : +76 °C (+169 °F) | | T_a : +76 °C (+169 °F) |
| P3 | = | T_p : +200 °C (+392 °F) | | T_a : +27 °C (+81 °F) |
| P4 | = | T_p : +200 °C (+392 °F) | | T_a : 0 °C (+32 °F) |
| P5 | = | T_p : 0 °C (+32 °F) | | T_a : 0 °C (+32 °F) |

Plastic housing; process temperature -20 to $+150$ °C (-4 to $+302$ °F)




A0032024

14 Plastic housing; process temperature -20 to $+150$ °C (-4 to $+302$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -20 °C (-4 °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P2 | = | T_p : | $+76$ °C ($+169$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P3 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | $+25$ °C ($+77$ °F) |
| P4 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | -20 °C (-4 °F) |
| P5 | = | T_p : | -20 °C (-4 °F) | | T_a : | -20 °C (-4 °F) |

i In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of -20 to $+150$ °C (-4 to $+302$ °F) is limited to 0 to $+150$ °C ($+32$ to $+302$ °F).

Restriction to a process temperature of 0 to $+150$ °C ($+32$ to $+302$ °F) with CSA C/US approval and plastic housing




A0049826

15 Plastic housing; process temperature 0 to $+150$ °C ($+32$ to $+302$ °F) with CSA C/US approval

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | 0 °C ($+32$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P2 | = | T_p : | $+76$ °C ($+169$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P3 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | $+25$ °C ($+77$ °F) |
| P4 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | 0 °C ($+32$ °F) |
| P5 | = | T_p : | 0 °C ($+32$ °F) | | T_a : | 0 °C ($+32$ °F) |

Plastic housing; process temperature -20 to $+200$ °C (-4 to $+392$ °F)




A0032024

16 Plastic housing; process temperature -20 to $+200$ °C (-4 to $+392$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -20 °C (-4 °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P2 | = | T_p : | $+76$ °C ($+169$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P3 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | $+27$ °C ($+81$ °F) |
| P4 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | -20 °C (-4 °F) |
| P5 | = | T_p : | -20 °C (-4 °F) | | T_a : | -20 °C (-4 °F) |

i In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of -20 to $+200$ °C (-4 to $+392$ °F) is limited to 0 to $+200$ °C ($+32$ to $+392$ °F).

Restriction to a process temperature of 0 to +200 °C (+32 to +392 °F) with CSA C/US approval and plastic housing




A0048826

17 Plastic housing; process temperature 0 to +200 °C (+32 to +392 °F) with CSA C/US approval

| | | | | |
|----|---|---------------------------|--|--------------------------|
| P1 | = | T_p : 0 °C (+32 °F) | | T_a : +76 °C (+169 °F) |
| P2 | = | T_p : +76 °C (+169 °F) | | T_a : +76 °C (+169 °F) |
| P3 | = | T_p : +200 °C (+392 °F) | | T_a : +27 °C (+81 °F) |
| P4 | = | T_p : +200 °C (+392 °F) | | T_a : 0 °C (+32 °F) |
| P5 | = | T_p : 0 °C (+32 °F) | | T_a : 0 °C (+32 °F) |

Plastic housing; process temperature -40 to +150 °C (-40 to +302 °F)




A0032024

18 Plastic housing; process temperature -40 to +150 °C (-40 to +302 °F)

| | | | | |
|----|---|---------------------------|--|--------------------------|
| P1 | = | T_p : -40 °C (-40 °F) | | T_a : +76 °C (+169 °F) |
| P2 | = | T_p : +76 °C (+169 °F) | | T_a : +76 °C (+169 °F) |
| P3 | = | T_p : +150 °C (+302 °F) | | T_a : +25 °C (+77 °F) |
| P4 | = | T_p : +150 °C (+302 °F) | | T_a : -40 °C (-40 °F) |
| P5 | = | T_p : -40 °C (-40 °F) | | T_a : -40 °C (-40 °F) |

i In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of -40 to +150 °C (-40 to +302 °F) is limited to 0 to +150 °C (+32 to +302 °F).

Restriction to a process temperature of 0 to +150 °C (+32 to +302 °F) with CSA C/US approval and plastic housing




A0048826

19 Plastic housing; process temperature 0 to +150 °C (+32 to +302 °F) with CSA C/US approval

| | | | | |
|----|---|---------------------------|--|--------------------------|
| P1 | = | T_p : 0 °C (+32 °F) | | T_a : +76 °C (+169 °F) |
| P2 | = | T_p : +76 °C (+169 °F) | | T_a : +76 °C (+169 °F) |
| P3 | = | T_p : +150 °C (+302 °F) | | T_a : +25 °C (+77 °F) |
| P4 | = | T_p : +150 °C (+302 °F) | | T_a : 0 °C (+32 °F) |
| P5 | = | T_p : 0 °C (+32 °F) | | T_a : 0 °C (+32 °F) |

Plastic housing; process temperature -40 to $+200$ °C (-40 to $+392$ °F)




A0032024

20 Plastic housing; process temperature -40 to $+200$ °C (-40 to $+392$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -40 °C (-40 °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P2 | = | T_p : | $+76$ °C ($+169$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P3 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | $+27$ °C ($+81$ °F) |
| P4 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | -40 °C (-40 °F) |
| P5 | = | T_p : | -40 °C (-40 °F) | | T_a : | -40 °C (-40 °F) |

i In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of -40 to $+200$ °C (-40 to $+392$ °F) is limited to 0 to $+200$ °C ($+32$ to $+392$ °F).

Restriction to a process temperature of 0 to $+200$ °C ($+32$ to $+392$ °F) with CSA C/US approval and plastic housing




A0049826

21 Plastic housing; process temperature 0 to $+200$ °C ($+32$ to $+392$ °F) with CSA C/US approval

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | 0 °C ($+32$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P2 | = | T_p : | $+76$ °C ($+169$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P3 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | $+27$ °C ($+81$ °F) |
| P4 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | 0 °C ($+32$ °F) |
| P5 | = | T_p : | 0 °C ($+32$ °F) | | T_a : | 0 °C ($+32$ °F) |

Aluminum housing, coated

Aluminum housing; process temperature -10 to $+150$ °C ($+14$ to $+302$ °F)




A0032024

22 Aluminum housing, coated; process temperature -10 to $+150$ °C ($+14$ to $+302$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -10 °C ($+14$ °F) | | T_a : | $+79$ °C ($+174$ °F) |
| P2 | = | T_p : | $+79$ °C ($+174$ °F) | | T_a : | $+79$ °C ($+174$ °F) |
| P3 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | $+53$ °C ($+127$ °F) |
| P4 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | -10 °C ($+14$ °F) |
| P5 | = | T_p : | -10 °C ($+14$ °F) | | T_a : | -10 °C ($+14$ °F) |

Aluminum housing; process temperature -10 to $+200$ °C ($+14$ to $+392$ °F)




A0032024

23 Aluminum housing, coated; process temperature -10 to $+200$ °C ($+14$ to $+392$ °F)

| | | | | |
|----|---|--------------------------------|--|-------------------------------|
| P1 | = | T_p : -10 °C ($+14$ °F) | | T_a : $+79$ °C ($+174$ °F) |
| P2 | = | T_p : $+79$ °C ($+174$ °F) | | T_a : $+79$ °C ($+174$ °F) |
| P3 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : $+47$ °C ($+117$ °F) |
| P4 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : -10 °C ($+14$ °F) |
| P5 | = | T_p : -10 °C ($+14$ °F) | | T_a : -10 °C ($+14$ °F) |

Aluminum housing; process temperature -20 to $+150$ °C (-4 to $+302$ °F)




A0032024

24 Aluminum housing, coated; process temperature -20 to $+150$ °C (-4 to $+302$ °F)

| | | | | |
|----|---|--------------------------------|--|-------------------------------|
| P1 | = | T_p : -20 °C (-4 °F) | | T_a : $+79$ °C ($+174$ °F) |
| P2 | = | T_p : $+79$ °C ($+174$ °F) | | T_a : $+79$ °C ($+174$ °F) |
| P3 | = | T_p : $+150$ °C ($+302$ °F) | | T_a : $+53$ °C ($+127$ °F) |
| P4 | = | T_p : $+150$ °C ($+302$ °F) | | T_a : -20 °C (-4 °F) |
| P5 | = | T_p : -20 °C (-4 °F) | | T_a : -20 °C (-4 °F) |

Aluminum housing; process temperature -20 to $+200$ °C (-4 to $+392$ °F)




A0032024

25 Aluminum housing, coated; process temperature -20 to $+200$ °C (-4 to $+392$ °F)

| | | | | |
|----|---|--------------------------------|--|-------------------------------|
| P1 | = | T_p : -20 °C (-4 °F) | | T_a : $+79$ °C ($+174$ °F) |
| P2 | = | T_p : $+79$ °C ($+174$ °F) | | T_a : $+79$ °C ($+174$ °F) |
| P3 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : $+47$ °C ($+117$ °F) |
| P4 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : -20 °C (-4 °F) |
| P5 | = | T_p : -20 °C (-4 °F) | | T_a : -20 °C (-4 °F) |

Aluminum housing; process temperature -40 to $+150$ °C (-40 to $+302$ °F)




A0032024

26 Aluminum housing, coated; process temperature -40 to $+150$ °C (-40 to $+302$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -40 °C (-40 °F) | | T_a : | $+79$ °C ($+174$ °F) |
| P2 | = | T_p : | $+79$ °C ($+174$ °F) | | T_a : | $+79$ °C ($+174$ °F) |
| P3 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | $+53$ °C ($+127$ °F) |
| P4 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | -40 °C (-40 °F) |
| P5 | = | T_p : | -40 °C (-40 °F) | | T_a : | -40 °C (-40 °F) |

Aluminum housing; process temperature -40 to $+200$ °C (-40 to $+392$ °F)




A0032024

27 Aluminum housing, coated; process temperature -40 to $+200$ °C (-40 to $+392$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -40 °C (-40 °F) | | T_a : | $+79$ °C ($+174$ °F) |
| P2 | = | T_p : | $+79$ °C ($+174$ °F) | | T_a : | $+79$ °C ($+174$ °F) |
| P3 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | $+47$ °C ($+117$ °F) |
| P4 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | -40 °C (-40 °F) |
| P5 | = | T_p : | -40 °C (-40 °F) | | T_a : | -40 °C (-40 °F) |

316L housing

316L housing; process temperature -10 to $+150$ °C ($+14$ to $+302$ °F)




A0032024

28 316L housing; process temperature -10 to $+150$ °C ($+14$ to $+302$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -10 °C ($+14$ °F) | | T_a : | $+77$ °C ($+171$ °F) |
| P2 | = | T_p : | $+77$ °C ($+171$ °F) | | T_a : | $+77$ °C ($+171$ °F) |
| P3 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | $+43$ °C ($+109$ °F) |
| P4 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | -10 °C ($+14$ °F) |
| P5 | = | T_p : | -10 °C ($+14$ °F) | | T_a : | -10 °C ($+14$ °F) |

316L housing; process temperature -10 to $+200$ °C ($+14$ to $+392$ °F)




A0032024

29 316L housing; process temperature -10 to $+200$ °C ($+14$ to $+392$ °F)

| | | | | |
|----|---|--------------------------------|--|-------------------------------|
| P1 | = | T_p : -10 °C ($+14$ °F) | | T_a : $+77$ °C ($+171$ °F) |
| P2 | = | T_p : $+77$ °C ($+171$ °F) | | T_a : $+77$ °C ($+171$ °F) |
| P3 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : $+38$ °C ($+100$ °F) |
| P4 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : -10 °C ($+14$ °F) |
| P5 | = | T_p : -10 °C ($+14$ °F) | | T_a : -10 °C ($+14$ °F) |

316L housing; process temperature -20 to $+150$ °C (-4 to $+302$ °F)




A0032024

30 316L housing; process temperature -20 to $+150$ °C (-4 to $+302$ °F)

| | | | | |
|----|---|--------------------------------|--|-------------------------------|
| P1 | = | T_p : -20 °C (-4 °F) | | T_a : $+77$ °C ($+171$ °F) |
| P2 | = | T_p : $+77$ °C ($+171$ °F) | | T_a : $+77$ °C ($+171$ °F) |
| P3 | = | T_p : $+150$ °C ($+302$ °F) | | T_a : $+43$ °C ($+109$ °F) |
| P4 | = | T_p : $+150$ °C ($+302$ °F) | | T_a : -20 °C (-4 °F) |
| P5 | = | T_p : -20 °C (-4 °F) | | T_a : -20 °C (-4 °F) |

316L housing; process temperature -20 to $+200$ °C (-4 to $+392$ °F)




A0032024

31 316L housing; process temperature -20 to $+200$ °C (-4 to $+392$ °F)

| | | | | |
|----|---|--------------------------------|--|-------------------------------|
| P1 | = | T_p : -20 °C (-4 °F) | | T_a : $+77$ °C ($+171$ °F) |
| P2 | = | T_p : $+77$ °C ($+171$ °F) | | T_a : $+77$ °C ($+171$ °F) |
| P3 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : $+38$ °C ($+100$ °F) |
| P4 | = | T_p : $+200$ °C ($+392$ °F) | | T_a : -20 °C (-4 °F) |
| P5 | = | T_p : -20 °C (-4 °F) | | T_a : -20 °C (-4 °F) |

316L housing; process temperature -40 to $+150$ °C (-40 to $+302$ °F)




A0032024

32 316L housing; process temperature range: -40 to $+150$ °C (-40 to $+302$ °F)

$P1 = T_p: -40$ °C (-40 °F) | $T_a: +77$ °C ($+171$ °F)
 $P2 = T_p: +77$ °C ($+171$ °F) | $T_a: +77$ °C ($+171$ °F)
 $P3 = T_p: +150$ °C ($+302$ °F) | $T_a: +43$ °C ($+109$ °F)
 $P4 = T_p: +150$ °C ($+302$ °F) | $T_a: -40$ °C (-40 °F)
 $P5 = T_p: -40$ °C (-40 °F) | $T_a: -40$ °C (-40 °F)

316L housing; process temperature -40 to $+200$ °C (-40 to $+392$ °F)




A0032024

33 316L housing; process temperature -40 to $+200$ °C (-40 to $+392$ °F)

$P1 = T_p: -40$ °C (-40 °F) | $T_a: +77$ °C ($+171$ °F)
 $P2 = T_p: +77$ °C ($+171$ °F) | $T_a: +77$ °C ($+171$ °F)
 $P3 = T_p: +200$ °C ($+392$ °F) | $T_a: +38$ °C ($+100$ °F)
 $P4 = T_p: +200$ °C ($+392$ °F) | $T_a: -40$ °C (-40 °F)
 $P5 = T_p: -40$ °C (-40 °F) | $T_a: -40$ °C (-40 °F)

316L housing, hygiene

316L housing, hygiene; process temperature -10 to $+150$ °C ($+14$ to $+302$ °F)




A0032024

34 316L housing, hygiene; process temperature -10 to $+150$ °C ($+14$ to $+302$ °F)

$P1 = T_p: -10$ °C ($+14$ °F) | $T_a: +76$ °C ($+169$ °F)
 $P2 = T_p: +76$ °C ($+169$ °F) | $T_a: +76$ °C ($+169$ °F)
 $P3 = T_p: +150$ °C ($+302$ °F) | $T_a: +41$ °C ($+106$ °F)
 $P4 = T_p: +150$ °C ($+302$ °F) | $T_a: -10$ °C ($+14$ °F)
 $P5 = T_p: -10$ °C ($+14$ °F) | $T_a: -10$ °C ($+14$ °F)

316L housing, hygiene; process temperature -10 to $+200$ °C ($+14$ to $+392$ °F)




A0032024

35 316L housing, hygiene; process temperature -10 to $+200$ °C ($+14$ to $+392$ °F)

$P1 = T_p: -10$ °C ($+14$ °F) | $T_a: +76$ °C ($+169$ °F)
 $P2 = T_p: +76$ °C ($+169$ °F) | $T_a: +76$ °C ($+169$ °F)
 $P3 = T_p: +200$ °C ($+392$ °F) | $T_a: +32$ °C ($+90$ °F)
 $P4 = T_p: +200$ °C ($+392$ °F) | $T_a: -10$ °C ($+14$ °F)
 $P5 = T_p: -10$ °C ($+14$ °F) | $T_a: -10$ °C ($+14$ °F)

316L housing, hygiene; process temperature -20 to $+150$ °C (-4 to $+302$ °F)




A0032024

36 316L housing, hygiene; process temperature -20 to $+150$ °C (-4 to $+302$ °F)

$P1 = T_p: -20$ °C (-4 °F) | $T_a: +76$ °C ($+169$ °F)
 $P2 = T_p: +76$ °C ($+169$ °F) | $T_a: +76$ °C ($+169$ °F)
 $P3 = T_p: +150$ °C ($+302$ °F) | $T_a: +41$ °C ($+106$ °F)
 $P4 = T_p: +150$ °C ($+302$ °F) | $T_a: -20$ °C (-4 °F)
 $P5 = T_p: -20$ °C (-4 °F) | $T_a: -20$ °C (-4 °F)

316L housing, hygiene; process temperature -20 to $+200$ °C (-4 to $+392$ °F)




A0032024

37 316L housing, hygiene; process temperature -20 to $+200$ °C (-4 to $+392$ °F)

$P1 = T_p: -20$ °C (-4 °F) | $T_a: +76$ °C ($+169$ °F)
 $P2 = T_p: +76$ °C ($+169$ °F) | $T_a: +76$ °C ($+169$ °F)
 $P3 = T_p: +200$ °C ($+392$ °F) | $T_a: +32$ °C ($+90$ °F)
 $P4 = T_p: +200$ °C ($+392$ °F) | $T_a: -20$ °C (-4 °F)
 $P5 = T_p: -20$ °C (-4 °F) | $T_a: -20$ °C (-4 °F)

316L housing, hygiene; process temperature -40 to $+150$ °C (-40 to $+302$ °F)




A0032024

38 316L housing, hygiene; process temperature range: -40 to $+150$ °C (-40 to $+302$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -40 °C (-40 °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P2 | = | T_p : | $+76$ °C ($+169$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P3 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | $+41$ °C ($+106$ °F) |
| P4 | = | T_p : | $+150$ °C ($+302$ °F) | | T_a : | -40 °C (-40 °F) |
| P5 | = | T_p : | -40 °C (-40 °F) | | T_a : | -40 °C (-40 °F) |

316L housing, hygiene; process temperature -40 to $+200$ °C (-40 to $+392$ °F)



A0032024

39 316L housing, hygiene; process temperature -40 to $+200$ °C (-40 to $+392$ °F)

| | | | | | | |
|----|---|---------|------------------------|--|---------|-----------------------|
| P1 | = | T_p : | -40 °C (-40 °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P2 | = | T_p : | $+76$ °C ($+169$ °F) | | T_a : | $+76$ °C ($+169$ °F) |
| P3 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | $+32$ °C ($+90$ °F) |
| P4 | = | T_p : | $+200$ °C ($+392$ °F) | | T_a : | -40 °C (-40 °F) |
| P5 | = | T_p : | -40 °C (-40 °F) | | T_a : | -40 °C (-40 °F) |

| | |
|---------------------|----------------------------------------------------------------|
| Storage temperature | ■ Without LCD display: -40 to $+90$ °C (-40 to $+194$ °F) |
| | ■ With LCD display: -40 to $+85$ °C (-40 to $+185$ °F) |

| | |
|---------------|-------------------------------|
| Climate class | DIN EN 60068-2-38 (test Z/AD) |
|---------------|-------------------------------|

| | |
|--------------------------------------------|-----------------------------------------------------|
| Installation height as per IEC61010-1 Ed.3 | Generally up to 5 000 m (16 404 ft) above sea level |
|--------------------------------------------|-----------------------------------------------------|

| | |
|----------------------|---------------------------------------------|
| Degree of protection | Testing according to IEC 60529 and NEMA 250 |
|----------------------|---------------------------------------------|

Housing

IP66/68, NEMA Type 4X/6P

IP68 test condition: 1.83 m under water for 24 hours.

Cable entries

- M20 coupling, plastic, IP66/68 NEMA Type 4X/6P
- M20 coupling, nickel-plated brass, IP66/68 NEMA Type 4X/6P
- M20 coupling, 316L, IP66/68 NEMA Type 4X/6P
- M20 coupling, hygiene, IP66/68/69 NEMA Type 4X/6P
- M20 thread, IP66/68 NEMA Type 4X/6P

- G1/2 thread, IP66/68 NEMA Type 4X/6P
If the G1/2 thread is selected, the device is delivered with an M20 thread as standard and a G1/2 adapter is included with the delivery, along with the corresponding documentation
- NPT 1/2 thread, IP66/68 NEMA Type 4X/6P
- M12 plug
 - When housing is closed and connecting cable is plugged in: IP66/67 NEMA Type 4X
 - When housing is open or connecting cable is not plugged in: IP20, NEMA Type 1

NOTICE**M12 plug: Loss of IP protection class due to incorrect installation!**

- ▶ The degree of protection only applies if the connecting cable used is plugged in and screwed tight.
- ▶ The degree of protection only applies if the connecting cable used is specified according to IP66/67 NEMA Type 4X.
- ▶ The protection classes are only maintained if the dummy cap is used or the cable is connected.

| | |
|--------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Vibration resistance | DIN EN 60068-2-64 / IEC 60068-2-64 for 5 to 2 000 Hz: 1.5 (m/s ²) ² /Hz |
| Electromagnetic compatibility (EMC) | <ul style="list-style-type: none"> ■ Electromagnetic compatibility as per EN 61326 series and NAMUR recommendation EMC (NE21) ■ Maximum measured error during EMC testing: < 0.5 % of the current digital measured value <p>For more details refer to the EU Declaration of Conformity.</p> |

Process

Process pressure range




The maximum pressure for the device depends on the lowest-rated component with regard to pressure (components are: process connection, optional mounted parts or accessories).

- ▶ Only operate the device within the specified limits for the components!
- ▶ MWP (Maximum Working Pressure): The MWP is specified on the nameplate. This value refers to a reference temperature of +20 °C (+68 °F) and may be applied to the device for an unlimited time. Note temperature dependence of MWP. For flanges, refer to the following standards for the permitted pressure values at higher temperatures: EN 1092-1 (with regard to their stability/temperature property, the materials 1.4435 and 1.4404 are grouped together under EN 1092-1; the chemical composition of the two materials can be identical), ASME B16.5, JIS B2220 (the latest version of the standard applies in each case). MWP data that deviate from this are provided in the relevant sections of the Technical Information.
- ▶ The Pressure Equipment Directive (2014/68/EU) uses the abbreviation **PS**. This corresponds to the maximum working pressure (MWP) of the device.

The following tables show the dependencies between the seal material, process temperature (T_p) and process pressure range for each process connection that can be selected for the antenna used.

Integrated antenna, PEEK, 20 mm (0.75 in)


Process connection M24 with process adapter, accessory enclosed

| | Seal | T_p | Process pressure range |
|-------------------------------------------------------------------------------------------------|-------------|---------------------------------|---------------------------------|
|  A0048027 | FKM Viton | -10 to +150 °C (+14 to +302 °F) | -1 to 20 bar (-14.5 to 290 psi) |
| | FKM Viton | -10 to +200 °C (+14 to +392 °F) | -1 to 20 bar (-14.5 to 290 psi) |
| | EPDM | -40 to +150 °C (-40 to +302 °F) | -1 to 20 bar (-14.5 to 290 psi) |
| | FFKM Kalrez | -20 to +150 °C (-4 to +302 °F) | -1 to 20 bar (-14.5 to 290 psi) |
| | FFKM Kalrez | -20 to +200 °C (-4 to +392 °F) | -1 to 20 bar (-14.5 to 290 psi) |




The pressure range may be further restricted in the event of a CRN approval.


Antenna, cladded flush mount, PTFE, 50 mm (2 in)*Process connection Tri-Clamp DN51 (2") ISO2852*

| | Seal | T _p | Process pressure range |
|-----------------------------------------------------------------------------------------------|--------------|---------------------------------|---------------------------------|
|  A0047838 | PTFE cladded | -40 to +150 °C (-40 to +302 °F) | -1 to 16 bar (-14.5 to 232 psi) |
| | PTFE cladded | -40 to +200 °C (-40 to +392 °F) | -1 to 16 bar (-14.5 to 232 psi) |

Process connection Tri-Clamp DN70-76.1 (3") ISO2852

| | Seal | T _p | Process pressure range |
|-----------------------------------------------------------------------------------------------|--------------|---------------------------------|---------------------------------|
|  A0047838 | PTFE cladded | -40 to +150 °C (-40 to +302 °F) | -1 to 14 bar (-14.5 to 203 psi) |
| | PTFE cladded | -40 to +200 °C (-40 to +392 °F) | -1 to 14 bar (-14.5 to 203 psi) |


Process connection slotted nut DIN11851 DN50 PN25

| | Seal | T _p | Process pressure range |
|-------------------------------------------------------------------------------------------------|--------------|---------------------------------|-----------------------------------|
|  A0050063 | PTFE cladded | -40 to +150 °C (-40 to +302 °F) | -1 to 25 bar (-14.5 to 362.6 psi) |
| | PTFE cladded | -40 to +200 °C (-40 to +392 °F) | -1 to 25 bar (-14.5 to 362.6 psi) |





The pressure range may be further restricted in the event of a CRN approval.

Antenna, cladded flush mount, PTFE, 80 mm (3 in)*Process connection Tri-Clamp DN101.6 (4") ISO2852*

| | Seal | T _p | Process pressure range |
|-------------------------------------------------------------------------------------------------|--------------|---------------------------------|---------------------------------|
|  A0047826 | PTFE cladded | -40 to +150 °C (-40 to +302 °F) | -1 to 14 bar (-14.5 to 203 psi) |
| | PTFE cladded | -40 to +200 °C (-40 to +392 °F) | -1 to 14 bar (-14.5 to 203 psi) |

Process connection slotted nut DIN11851 DN80 PN25

| | Seal | T _p | Process pressure range |
|-----------------------------------------------------------------------------------------------|-------------|---------------------------------|-----------------------------------|
|  A0047825 | PTFE cladde | -40 to +150 °C (-40 to +302 °F) | -1 to 25 bar (-14.5 to 362.6 psi) |
| | PTFE cladde | -40 to +200 °C (-40 to +392 °F) | -1 to 25 bar (-14.5 to 362.6 psi) |

 The pressure range may be further restricted in the event of a CRN approval.

Dielectric constant


For liquids
 $\epsilon_r \geq 1.2$
Contact Endress+Hauser for applications with lower dielectric constants than indicated.


Mechanical construction

Dimensions

 The dimensions of the individual components must be added together for the total dimensions.


Single compartment housing, plastic



 40 Dimensions of single compartment housing, plastic (PBT). Unit of measurement mm (in)
1 Height with cover comprising plastic sight glass
2 Cover without sight glass

A0048768

Single compartment housing, aluminum




A0038380

41 Dimensions of single compartment housing, aluminum. Unit of measurement mm (in)

- 1 Height with cover comprising glass sight glass (devices for Ex d/XP, dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass

Single compartment housing, 316L hygiene




A0050364

42 Dimensions of single compartment housing, 316L hygiene. Unit of measurement mm (in)

- 1 Height with cover comprising glass sight glass (dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass


Dual compartment housing, aluminum



43 Dimensions of dual compartment housing, aluminum. Unit of measurement mm (in)


- 1 Height with cover comprising glass sight glass (devices for Ex d/XP, dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass

Dual compartment housing, L-shaped, aluminum or 316 L



44 Dimensions of L-shaped dual compartment housing. Unit of measurement mm (in)

- 1 Height with cover comprising glass sight glass (devices for Ex d/XP, dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass

Integrated antenna, PEEK, 20 mm / M24×1.5

A0046492

45 Dimensions of integrated antenna, PEEK, 20 mm / M24×1.5. Unit of measurement mm (in)

A Process temperature version ≤ 150 °C (302 °F)

B Process temperature version ≤ 200 °C (392 °F)


R Reference point of measurement

1 Bottom edge of housing

L1 127 mm (5.00 in); version with Ex d or XP approval +5 mm (+0.20 in)

L2 139 mm (5.47 in); version with Ex d or XP approval +5 mm (+0.20 in)

Antenna, cladded flush mount, PTFE, 50 mm (2 in), slotted nut DIN11851




A0046496

46 Dimensions of antenna, cladded flush mount, PTFE, 50 mm (2 in), slotted nut DIN11851. Unit of measurement mm (in)

- A Process temperature version $\leq 150^{\circ}\text{C}$ (302°F)
- B Process temperature version $\leq 200^{\circ}\text{C}$ (392°F)
- R Reference point of measurement
- 1 Bottom edge of housing
- L1 118 mm (4.65 in); version with Ex d or XP approval +5 mm (+0.20 in)
- L2 130 mm (5.12 in); version with Ex d or XP approval +5 mm (+0.20 in)


Antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN40-51 (2") ISO2852



48 Dimensions of antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN51 (2") ISO2852.
Unit of measurement mm (in)

- A Process temperature version $\leq 150\text{ }^{\circ}\text{C}$ (302 $^{\circ}\text{F}$)
- B Process temperature version $\leq 200\text{ }^{\circ}\text{C}$ (392 $^{\circ}\text{F}$)
- R Reference point of measurement
- 1 Bottom edge of housing
- L1 116 mm (4.57 in); version with Ex d or XP approval +5 mm (+0.20 in)
- L2 128 mm (5.04 in); version with Ex d or XP approval +5 mm (+0.20 in)

i Process connection suitable for
DN51 nominal diameter and pipe inner diameter 48.6 mm (1.91 in)

Antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN70-76.1 (3") ISO2852

A0046484

49 Dimensions of antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN70-76.1 (3") ISO2852. Unit of measurement mm (in)

A Process temperature version ≤ 150 °C (302 °F)

B Process temperature version ≤ 200 °C (392 °F)

R Reference point of measurement

1 Bottom edge of housing


L1 116 mm (4.57 in); version with Ex d or XP approval +5 mm (+0.20 in)

L2 128 mm (5.04 in); version with Ex d or XP approval +5 mm (+0.20 in)



Process connection suitable for

- DN70 nominal diameter with pipe inner diameter 66.8 mm (2.63 in)
- DN76.1 nominal diameter with pipe inner diameter 72.9 mm (2.87 in)

Antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp DN101.6 (4") ISO2852

50 Dimensions of antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp DN101.6 (4") ISO2852.
Unit of measurement mm (in)

- A Process temperature version $\leq 150\text{ }^{\circ}\text{C}$ (302 $^{\circ}\text{F}$)
 B Process temperature version $\leq 200\text{ }^{\circ}\text{C}$ (392 $^{\circ}\text{F}$)
 R Reference point of measurement
 1 Bottom edge of housing
 L1 155 mm (6.10 in); version with Ex d or XP approval +5 mm (+0.20 in)
 L2 167 mm (6.57 in); version with Ex d or XP approval +5 mm (+0.20 in)

i Process connection suitable for
 DN101.6 nominal diameter with pipe inner diameter 97.6 mm (3.84 in)

Weight

i The weights of the individual components must be added together for the total weight.

Housing

Weight including electronics and display.

Single compartment housing

- Plastic: 0.5 kg (1.10 lb)
- Aluminum: 1.2 kg (2.65 lb)
- 316L hygiene: 1.2 kg (2.65 lb)

Dual compartment housing

Aluminum: 1.4 kg (3.09 lb)

Dual compartment housing, L-form

- Aluminum: 1.7 kg (3.75 lb)
- Stainless steel: 4.5 kg (9.9 lb)

Antenna and process connection adapter

i The flange weight (316/316L) depends on the selected standard and sealing surface.
 Details -> TI00426F or in the relevant standard

i The heaviest version is indicated for the antenna weights

Integrated antenna, PEEK, 20 mm (0.75 in)

1.2 kg (2.65 lb)

Antenna, cladded flush mount, PTFE, 50 mm (2 in)

2.2 kg (4.85 lb) for process connection slotted nut DIN11851

Antenna, cladded flush mount, PTFE, 80 mm (3 in)

3.4 kg (7.50 lb) for process connection slotted nut DIN11851

Materials**Materials not in contact with process***Plastic housing*

- Housing: PBT/PC
- Dummy cover: PBT/PC
- Cover with sight glass: PBT/PC and PC
- Cover seal: EPDM
- Potential equalization: 316L
- Seal under potential equalization: EPDM
- Plug: PBT-GF30-FR
- M20 cable gland: PA
- Seal on plug and cable gland: EPDM
- Threaded adapter as replacement for cable glands: PA66-GF30
- Nameplate: plastic foil
- TAG plate: plastic foil, metal or provided by customer

Aluminum housing, coated

- Housing: EN AC-43400 aluminum
- Housing coating, cover: Polyester
- Dummy cover: EN AC-43400 aluminum
- EN AC-43400 aluminum cover with Lexan 943A PC sight glass
EN AC-43400 aluminum cover with borosilicate sight glass; can be ordered as an accessory optionally
For Ex d, dust Ex applications, the sight glass is always made from borosilicate.
- Cover seal materials: HNBR
- Cover seal materials: FVMQ (only for low temperature version)
- Nameplate: plastic foil
- TAG plate: plastic foil, stainless steel or provided by customer
- M20 cable glands: select material (stainless steel, nickel-plated brass, polyamide)

Stainless steel housing, 316L


- Housing: stainless steel 316L (1.4409)
- Dummy cover: stainless steel 316L (1.4409)
- 316L (1.4409) stainless steel cover with borosilicate window
- Cover seal materials: FVMQ (only for low temperature version)
- Cover seal materials: HNBR
- Nameplate: stainless steel housing, labeled directly
- TAG plate: plastic foil, stainless steel or provided by the customer
- M20 cable glands: select material (stainless steel, nickel-plated brass, polyamide)

Stainless steel housing, 316L hygiene

- Housing: stainless steel 316L (1.4404)
- Dummy cover: stainless steel 316L (1.4404)
- 316L (1.4404) stainless steel cover with PC Lexan 943A window
316L (1.4404) stainless steel cover with borosilicate window; can be optionally ordered as an enclosed accessory
For Dust-Ex applications, the window is always made from borosilicate.
- Cover seal materials: EPDM
- Nameplate: stainless steel housing, labeled directly
- TAG plate: plastic foil, stainless steel or provided by the customer
- M20 cable glands: select material (stainless steel, nickel-plated brass, polyamide)

Materials in contact with the medium

Integrated antenna, PEEK, 20 mm / M24×1.5




A0046101

51 Material; integrated antenna, PEEK, 20 mm / M24×1.5

- 1 Antenna: PEEK, seal material can be selected (order option)
- 2 Process connection: 316L / 1.4404
- 3 Housing adapter: 316L / 1.4404

Antenna, cladded flush mount, 50 mm (2 in), slotted nut DIN11851




A0046619

52 Material; antenna, cladded flush mount, 50 mm (2 in), slotted nut DIN11851

- 1 Antenna: PTFE, seal material PTFE cladding
- 2 DIN11851 slotted nut: 304L / 1.4307
- 3 Antenna adapter: 316L / 1.4404
- 4 Housing adapter: 316L / 1.4404

Antenna, cladded flush mount, 80 mm (3 in), slotted nut DIN11851




A0046620

53 Material; antenna, cladded flush mount, 80 mm (3 in), slotted nut DIN11851. Unit of measurement mm (in)

- 1 Antenna: PTFE, seal material PTFE cladding
- 2 DIN11851 slotted nut: 304L / 1.4307
- 3 Antenna adapter: 316L / 1.4404
- 4 Housing adapter: 316L / 1.4404

Antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp ISO2852




A0046607

54 Material; antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp ISO2852. Unit of measurement mm (in)

- 1 Antenna: PTFE, seal material PTFE cladding
- 2 Antenna adapter: 316L / 1.4404
- 3 Housing adapter: 316L / 1.4404

Antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp ISO2852



A0046608

■ 55 Material; antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp ISO2852

1 Antenna: PTFE, seal material PTFE cladding

2 Antenna adapter: 316L / 1.4404

3 Housing adapter: 316L / 1.4404

Display and user interface

Operation concept

Operator-oriented menu structure for user-specific tasks

- User navigation
- Diagnosis
- Application
- System

Quick and safe commissioning

- Interactive wizard with graphical interface for guided commissioning in FieldCare, DeviceCare or DTM and PDM-based tools from third-party users or SmartBlue
- Menu guidance with brief descriptions of the individual parameter functions
- Standardized operation at the device and in the operating tools

Integrated HistoROM data memory

- Adoption of data configuration when electronics modules are replaced
- Up to 100 event messages recorded in the device
- A reference signal curve is saved during commissioning for later use as a reference during operation

Efficient diagnostics increase measurement reliability

- Remedial measures are integrated in plain text
- Diverse simulation options

Bluetooth module (optionally integrated in local display)


- Easy and fast setup via SmartBlue app or PC with DeviceCare from version 1.07.00 or FieldXpert SMT70
- No additional tools or adapters needed
- Encrypted single point-to-point data transmission (tested by Fraunhofer Institute) and password-protected communication via *Bluetooth®* wireless technology

Languages

The operating language of the local display (optional) can be selected via the Product Configurator. The local display is delivered with English from the factory if a different language was not selected. The operating language can be changed subsequently via the **Language** parameter.

Local operation

Local operation with 3 keys (⏏, ⏏, ⏏) on the display.



A0046640



The operating elements are also accessible in the various hazardous areas.

Local display


Device display (optional)

Functions

- Display measured values, also fault and notice messages
- Background lighting, which switches from green to red in the event of an error
- The device display can be removed for easier operation




The device displays are available with the additional option of Bluetooth® wireless technology.



A0043059

56 Segment display without keys



A0039284


57 Graphic display

1 Optical operating keys


Permitted ambient temperature for the display: -20 to $+70$ °C (-4 to $+158$ °F)

The readability of the display may be impaired at temperatures outside the temperature range.

Local operation with 3 keys (+, ESC, E) on the display.




A0046640

 The operating elements are also accessible in the various hazardous areas.

Installation position of device display exchangeable


The installation position of the display can be changed in the case of the dual compartment housing, L-form.



A004B401

Remote operation


Via PROFIBUS PA protocol



A0050944

- 1 Segment coupler
- 2 Computer with PROFlusb and operating tool (e.g. DeviceCare/FieldCare)
- 3 PLC (programmable logic controller)
- 4 Transmitter
- 5 Additional functions (valves etc.)

Via service interface (CDI)



A0039148

- 1 Computer with FieldCare/DeviceCare operating tool
- 2 Commubox FXA291
- 3 Service interface (CDI) of the measuring device (= Endress+Hauser Common Data Interface)

Operation via Bluetooth® wireless technology (optional)

Prerequisite

- Measuring device with Bluetooth display
- Smartphone or tablet with SmartBlue app or PC with DeviceCare, version 1.07.00 and higher, or FieldXpert SMT70

The connection has a range of up to 25 m (82 ft). The range can vary depending on environmental conditions such as attachments, walls or ceilings.

System integration

According to EN 50170 Volume 2, IEC 61158-2 (MBP) type 1 PROFIBUS PA Profile Version 3.02

| | |
|----------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Supported operating tools | Smartphone or tablet with Endress+Hauser SmartBlue (app), DeviceCare, version 1.07.00 and higher, FieldCare, DTM, and PDM. |
|----------------------------------|----------------------------------------------------------------------------------------------------------------------------|

Certificates and approvals

Current certificates and approvals for the product are available at www.endress.com on the relevant product page:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Downloads**.

| | |
|-------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CE mark | <p>The measuring system meets the legal requirements of the applicable EU directives. These are listed in the corresponding EU Declaration of Conformity together with the standards applied.</p> <p>The manufacturer confirms successful testing of the device by affixing to it the CE mark.</p> |
| RoHS | The measuring system meets the substance restrictions of the Directive on the Restriction of the Use of Certain Hazardous Substances 2011/65/EU (RoHS 2) and the Delegated Directive (EU) 2015/863 (RoHS 3). |
| RCM marking | <p>The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products bear the RCM marking on the nameplate.</p> <div data-bbox="948 1068 1074 1162" data-label="Image"> </div> |
| Ex approvals | <p>Additional safety instructions must be followed for use in hazardous areas. Please refer to the separate "Safety Instructions" (XA) document included in the delivery. Reference to the applicable XA can be found on the nameplate.</p> <p>Explosion-protected smartphones and tablets</p> <p>If used in hazardous areas, mobile end devices with an Ex approval must be used.</p> |
| Pressure equipment with permitted pressure ≤ 200 bar (2 900 psi) | <p>Pressure instruments with a process connection that does not have a pressurized housing do not fall within the scope of the Pressure Equipment Directive, irrespective of the maximum allowable pressure.</p> <p>Reasons:</p> <p>According to Article 2, point 5 of EU Directive 2014/68/EU, pressure accessories are defined as "devices with an operational function and having pressure-bearing housings".</p> <p>If a pressure instrument does not have a pressure-bearing housing (no identifiable pressure chamber of its own), there is no pressure accessory present within the meaning of the Directive.</p> |
| Radio approval | Displays with Bluetooth LE have radio licenses according to CE and FCC. The relevant certification information and labels are provided on display. |
| EN 302372 radio standard | The devices comply with the TLPR (Tanks Level Probing Radar) radio standard EN 302372 and are permitted for use in closed vessels. Points a to f in Annex E of EN 302372 must be observed for the installation. |

| | |
|------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| FCC | <p>This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.</p> <p>[Any] changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.</p> <p>The devices are compliant with the FCC Code of Federal Regulations, CFR 47, Part 15, Sections 15.205, 15.207, 15.209.</p> |
| Industry Canada | <p>Canada CNR-Gen Section 7.1.3</p> <p>This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions: (1) This device may not interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.</p> <p><i>Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes : (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.</i></p> <p>[Any] changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.</p> <ul style="list-style-type: none"> ■ The installation of the LPR/TLPR device shall be done by trained installers, in strict compliance with the manufacturer's instructions. ■ The use of this device is on a "no-interference, no-protection" basis. That is, the user shall accept operations of high-powered radar in the same frequency band which may interfere with or damage this device. However, devices found to interfere with primary licensing operations will be required to be removed at the user's expense. ■ This device shall be installed and operated in a completely enclosed container to prevent RF emissions, which can otherwise interfere with aeronautical navigation. ■ The installer/user of this device shall ensure that it is at least 10 km from the Dominion Astrophysical Radio Observatory (DRAO) near Penticton, British Columbia. The coordinates of the DRAO are latitude 49°19'15" N and longitude 119°37'12" W. For devices not meeting this 10 km separation (e.g., those in the Okanagan Valley, British Columbia,) the installer/user must coordinate with, and obtain the written concurrence of, the Director of the DRAO before the equipment can be installed or operated. The Director of the DRAO may be contacted at 250-497-2300 (tel.) or 250-497-2355 (fax). (Alternatively, the Manager, Regulatory Standards Industry Canada, may be contacted.) |
| External standards and guidelines | <ul style="list-style-type: none"> ■ EN 60529 Degrees of protection provided by enclosures (IP code) ■ EN 61010-1 Safety requirements for electrical equipment for measurement, control and laboratory use ■ IEC/EN 61326 Emission in accordance with Class A requirements A; Electromagnetic compatibility (EMC requirements) ■ NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment ■ NAMUR NE 53 Software of field devices and signal-processing devices with digital electronics ■ NAMUR NE 107 Status categorization in accordance with NE 107 ■ NAMUR NE 131 Requirements for field devices for standard applications |

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

1. Select the product using the filters and search field.
2. Open the product page.

3. Select **Configuration**.




Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Calibration

Factory calibration certificate

The calibration points are spread evenly over the measuring range (0 to 100 %). The Empty calibration **E** and Full calibration **F** must be specified to define the measuring range. If this information is missing, antenna-dependent default values are used instead.



A0032643

R Reference point of measurement

A Minimum distance between reference point *R* and 100% mark

E Empty calibration

F Full calibration

Measuring range restrictions

The following restrictions must be considered when selecting **E** and **F**:

- Minimum distance between reference point **R** and **100%** mark
 $A \geq 400 \text{ mm (16 in)}$
- Minimum span
 $F \geq 45 \text{ mm (1.77 in)}$
- Maximum value for Empty calibration
 $E \geq 450 \text{ mm (17.72 in)}$ (maximum 50 m (164 ft))



- Calibration takes place under reference conditions .

■ The selected values for Empty calibration and Full calibration are only used to create the factory calibration certificate. Afterwards, the values are reset to the default values specific for the antenna. If values other than the default values are required, they must be ordered as a customized empty/full calibration.


Product Configurator → Optional → Service → **Customized empty/full calibration**

Service

Services that can be selected via the product structure in the Product Configurator include.

- Cleaned of oil+grease (wetted)
- PWIS-free (paint-wetting impairment substances)
- ANSI Safety Red coating, coated housing cover
- Set damping
- Bluetooth communication is disabled on delivery
- Customized empty/full calibration
- Product documentation on paper

A printed (hard copy) version of test reports, declarations and inspection certificates can optionally be ordered via the **Service** feature, **Product documentation on paper** option. The documents can be selected via the **Test, certificate, declaration** feature and are then provided with the device upon delivery.

| | |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Test, certificate, declaration | <p>All test reports, declarations and inspection certificates are provided electronically in the <i>Device Viewer</i>:</p> <p>Enter the serial number from the nameplate (www.endress.com/deviceviewer)</p> |
| Identification | <p>Measuring point (tag)</p> <p>The device can be ordered with a tag name.</p> <p>Location of tag name</p> <p>In the additional specification, select:</p> <ul style="list-style-type: none"> ■ Stainless steel tag plate ■ Paper adhesive label ■ Tag provided by the customer ■ RFID TAG ■ RFID TAG + stainless steel tag plate ■ RFID TAG + paper adhesive label ■ RFID TAG + TAG provided by the customer ■ IEC 61406 stainless steel TAG ■ IEC 61406 stainless steel TAG + NFC TAG ■ IEC 61406 stainless steel TAG, stainless steel TAG ■ IEC 61406 stainless steel TAG + NFC, stainless steel TAG ■ IEC 61406 stainless steel TAG, plate provided ■ IEC 61406 stainless steel TAG + NFC, plate provided <p>Definition of tag name</p> <p>In the additional specification, specify: 3 lines of maximum 18 characters each</p> <p>The specified tag name appears on the selected plate and/or on the RFID TAG.</p> <p>Presentation in the SmartBlue app</p> <p>The first 18 characters of the tag name</p> <p>The tag name can always be changed specifically for the measuring point via Bluetooth.</p> <p>Display in electronic nameplate (ENP)</p> <p>The first 18 characters of the tag name</p> <p>Display in PROFIBUS PA</p> <p>The first 18 characters of the tag name are part of the electronic nameplate (ENP) and are also used as TAG_DESC in accordance with the PA Profile 3.02.</p> <p> For further information, please refer to SD01502F, SD02796P</p> <p>Available in the Download Area of the Endress+Hauser website (www.endress.com/downloads).</p> |

Application packages

| | |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Heartbeat Technology | <p>The Heartbeat Verification + Monitoring application package offers diagnostic functionality through continuous self-monitoring, the transmission of additional measured variables to an external Condition Monitoring system and the in-situ verification of devices in the application.</p> <p>The application package can be ordered together with the device or can be activated subsequently with an activation code. Detailed information on the order code is available via the Endress+Hauser website www.endress.com or from your local Endress+Hauser Sales Center.</p> <p>Heartbeat Verification</p> <p>Heartbeat Verification is carried out on request and supplements self-monitoring, which is performed continuously, by carrying out further tests. During verification, the system checks whether the device components comply with the factory specifications. Both the sensor and the electronics modules are included in the tests.</p> <p>Heartbeat Verification confirms the device function on request within the specified measuring tolerance with a total test coverage TTC (Total Test Coverage) in percent.</p> <p>Heartbeat Verification meets the requirements for metrological traceability in accordance with ISO 9001 (ISO9001:2015 Section 7.1.5.2).</p> |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

The result of the verification is either Passed or Failed. The verification data are saved in the device and optionally archived on a PC with the FieldCare asset management software or in the Netilion Library. Based on this data, a verification report is generated automatically to ensure that traceable documentation of the verification results is available.

Heartbeat Monitoring

Foam detection wizard and **Build-up detection** wizard are available, process windows can be configured. Furthermore, additional monitoring parameters can be displayed and used for predictive maintenance or application optimization.

"Foam detection" wizard

This wizard configures the automatic foam detection.

Foam detection can be linked to a output variable or status information e.g. to control a sprinkler used to dissolve the foam. It is also possible to monitor the foam increase in a so called foam index. The foam index can also be linked to a output variable and can be shown on the display.

Preparation:

The Foam monitoring initialization should only be done without or less foam.

Areas of application

- Measurement in liquids
- Reliable detection of foam on the medium

"Build-up detection" wizard

This wizard configures the build-up detection.

Basic idea:

The build-up detection can, for example, be linked to a compressed-air system to clean the antenna. With the build-up monitoring the maintenance cycles can be optimized.

Preparation:

The build-up monitoring initialization should only be done without or less build-up.

Areas of application

- Measurement in liquids and solids
- Reliable detection of buildup on the antenna

Detailed description



Special Documentation SD03093F


Accessories

Weather protection cover 316L

The weather protection cover can be ordered together with the device via the "Accessory enclosed" product structure.

It is used to protect against direct sunlight, precipitation and ice.

Weather protection cover 316L is suitable for the dual compartment housing made of aluminum or 316L. The delivery includes the holder for direct mounting on the housing.



A0039231

58 Dimensions. Unit of measurement mm (in)

Material

- Weather protection cover: 316L
- Clamping screw: A4
- Holder: 316L

Order number for accessories:


71438303

Plastic weather protection cover

The weather protection cover can be ordered together with the device via the "Accessory enclosed" product structure.

It is used to protect against direct sunlight, precipitation and ice.

The plastic weather protection cover is suitable for the single compartment housing made of aluminum. The delivery includes the holder for direct mounting on the housing.



A0038280

59 Dimensions. Unit of measurement mm (in)

Material

Plastic


Order number for accessories:

71438291

Remote display FHX50B

The remote display is ordered via the Product Configurator.

If the remote display is to be used, the device version **Prepared for display FHX50B** must be ordered.



A0046692

- A Plastic single compartment housing, remote display
 B Aluminum single compartment housing, remote display
 C Single compartment housing, 316L hygiene, remote display
 D Device side, plastic single compartment housing prepared for display FHX50B
 E Device side, aluminum single compartment housing prepared for display FHX50B
 F Device side, dual compartment housing, L-form, prepared for display FHX50B
 G Device side, single compartment housing, 316L hygiene, prepared for display FHX50B

Material of single compartment housing, remote display

- Aluminum
- Plastic

Degree of protection:

- IP68 / NEMA 6P
- IP66 / NEMA 4x

Connecting cable:

- Connecting cable (option) up to 30 m (98 ft)
- Customer-supplied standard cable up to 60 m (197 ft)
 Recommendation: EtherLine®-P CAT.5e from LAPP.

Specification of customer-supplied connecting cable

Push-in CAGE CLAMP®, connection technology, push actuation

- Conductor cross-section:
 - Solid conductor 0.2 to 0.75 mm² (24 to 18 AWG)
 - Fine-stranded conductor 0.2 to 0.75 mm² (24 to 18 AWG)
 - Fine-stranded conductor; with insulated ferrule 0.25 to 0.34 mm²
 - Fine-stranded conductor; without insulated ferrule 0.25 to 0.34 mm²
- Stripping length 7 to 9 mm (0.28 to 0.35 in)
- Outer diameter: 6 to 10 mm (0.24 to 0.4 in)
- Maximum cable length: 60 m (197 ft)

Ambient temperature:

- -40 to +80 °C (-40 to +176 °F)
- Option: -50 to +80 °C (-58 to +176 °F)

Gas-tight feedthrough

Chemically inert glass feedthrough, which prevents gases from entering the electronics housing.
 Can optionally be ordered as "Accessory mounted" via the product structure.

Process adapter M24



For details, refer to TI00426F/00/EN "Weld-in adapters, process adapters and flanges".

Field Xpert SMT70

Universal, high-performance tablet PC for device configuration in Ex Zone 2 and non-Ex areas



For details, see "Technical Information" TI01342S

DeviceCare SFE100

Configuration tool for HART, PROFIBUS and FOUNDATION Fieldbus field devices



Technical Information TI01134S

FieldCare SFE500

FDT-based plant asset management tool


It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.



Technical Information TI00028S

RID14

8-channel field indicator for fieldbus systems



A0011631


Displays 8 process- or calculated values for FOUNDATION Fieldbus™ or PROFIBUS® PA protocol



Technical Information TI00145R and Operating Instructions BA01267K

RID16

8-channel field indicator for fieldbus systems



A0011634


Displays 8 process- or calculated values for FOUNDATION Fieldbus™ or PROFIBUS® PA protocol



Technical Information TI00146R and Operating Instructions BA00284R

Fieldgate SFG500

Smart Ethernet/PROFIBUS gateway



A0028262

Parallel access to PROFIBUS networks, PROFIBUS and HART device status monitoring

Ethernet gateway basic mode with integrated web server and adaptive PROFIBUS master, Class 2 for communication with PROFIBUS devices.

Order number for accessories:

71116672



Operating Instructions BA01579S

Documentation




For an overview of the scope of the associated Technical Documentation, refer to the following:

- *Device Viewer* (www.endress.com/deviceviewer): Enter the serial number from the nameplate
- *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

Document function

The following documentation may be available depending on the version ordered:

| Document type | Purpose and content of the document |
|------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Technical Information (TI) | Planning aid for your device The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device. |
| Brief Operating Instructions (KA) | Guide that takes you quickly to the 1st measured value The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning. |
| Operating Instructions (BA) | Your reference document The Operating Instructions contain all the information that is required in the various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal. |
| Description of Device Parameters (GP) | Reference for your parameters The document provides a detailed explanation of each individual parameter. The description is aimed at those who work with the device over the entire life cycle and perform specific configurations. |
| Safety Instructions (XA) | Depending on the approval, safety instructions for electrical equipment in hazardous areas are also supplied with the device. The Safety Instructions are an integral part of the Operating Instructions.  Information on the Safety Instructions (XA) relevant to the device is provided on the nameplate. |
| Supplementary device-dependent documentation (SD/FY) | Always comply strictly with the instructions in the relevant supplementary documentation. The supplementary documentation is an integral part of the device documentation. |

Registered trademarks

PROFIBUS®

PROFIBUS and the associated trademarks (The Association Trademark, the Technology Trademarks, the Certification Trademark and the Certified by PI Trademark) are registered trademarks of the PROFIBUS User Organization e.V. (Profibus User Organization), Karlsruhe - Germany

Bluetooth®

The *Bluetooth*® word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Endress+Hauser is under license. Other trademarks and trade names are those of their respective owners.

Apple®

Apple, the Apple logo, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc.

Android®

Android, Google Play and the Google Play logo are trademarks of Google Inc.

KALREZ®, VITON®

Registered trademarks of DuPont Performance Elastomers L.L.C., Wilmington, DE USA

TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA



www.addresses.endress.com
