Safety Instructions Soliphant M FTM50, FTM51, FTM52

Ex ta/tb IIIC T160°C...T310°C Da/Db Ex ta/tb [ia Da] IIIC T83°C Da/Db Ex tb [ia Da] IIIC T83°C Db







Soliphant M FTM50, FTM51, FTM52

Table of contents

About this document	4
Associated documentation	. 4
Supplementary documentation	. 4
Manufacturer's certificates	. 4
Manufacturer address	4
Extended order code	. 4
Safety instructions: General	. 7
Safety instructions: Special conditions	8
Safety instructions: Installation	8
Temperature tables	11
Connection data	19

About this document	This document has been translated into several languages. Legally determined is solely the English source text.
Associated documentation	This document is an integral part of the following Operating Instructions: • KA00229F/00 (FTM50, FTM51) • KA00230F/00 (FTM52)
Supplementary documentation	 Explosion-protection brochure: CP00021Z/11 The Explosion-protection brochure is available: In the download area of the Endress+Hauser website: www.endress.com -> Downloads -> Brochures and Catalogs -> Text Search: CP00021Z On the CD for devices with CD-based documentation
Manufacturer's certificates	NEPSI Declaration of Conformity Certificate number: GYJ21.3324 Affixing the certificate number certifies conformity with the following standards (depending on the device version): • GB/T 3836.1-2021 • GB/T 3836.4-2021 • GB/T 3836.31-2021
Manufacturer address	Endress+Hauser SE+Co. KG Hauptstraße 1 79689 Maulburg, Germany Address of the manufacturing plant: See nameplate.
Extended order code	The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.

Structure of the extended order code

FTM5x	-	*****	+	A*B*C*D*E*F*G*
(Device		(Basic		(Optional
type)		specifications)		specifications)

* = Placeholder

At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.

Basic specifications

The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions.

Optional specifications

The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = Test, Certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate).

More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.

Extended order code: Soliphant M

Device type FTM50, FTM51, FTM52

Basic specifications

Position 1 (Approval)			
Selected option	Description		
FTM50 8 FTM51	NEPSI Ex ta/tb IIIC T160°CT310°C Da/Db $^{1)}$ NEPSI Ex tb [ia Da] IIIC T83°C Db $^{2)}$		
FTM52 8	NEPSI Ex ta/tb [ia Da] IIIC T83°C Da/Db NEPSI Ex tb [ia Da] IIIC T83°C Db ²⁾		

1) Depending on Position 11

2) Only in connection with Position 7 = D, E, G, H

Position 6	Position 6 (Electronics, Output)			
Selected option		Description		
FTM5x	1	FEM51; 2-wire 19-253VAC		
	2	FEM52; 3-wire PNP 10-55VDC		
	4	FEM54; relay DPDT, 19-253VAC/55VDC		
	5	FEM55; 8/16mA, 11-35VDC		

Position 7 (Type of Probe)			
Selected opt	ion	Description	
FTM5x	А	Compact	
	D, E	Cable > separate enclosure	
	G, H	Cable, armoured > separate enclosure	

Position 8 (Position 8 (Housing)			
Selected op	tion	Description		
FTM5x	Н	T13 Alu IP66/68 NEMA Type 4X/6P Encl., separate conn. compartment		
	3	F17 Alu IP66/67 NEMA Type 4X Encl.		
	5	F13 Alu IP66/68 NEMA Type 4X/6P Encl.		
	6	F27 316L IP67/68 NEMA Type 4X/6P Encl.		
	7	F15 316L hygiene IP66/67 NEMA Type 4X Encl.		

Position 11 (Additional Option 2)			
Selected op	otion	Description	
FTM50	А	Not selected	
FTM51	С	EN10204-3.1 material (wetted parts), inspection certificate	
	D, E	Temp. separator ≤150°C	
	F, H	High temperature ≤280°C	
	J, K	High temperature <230°C	
	Y	Special version: High temperature ≤300°C	
FTM52	А	Not selected	

Optional specifications

No options specific to hazardous locations are available.

Safety instructions: General	 The device is intended to be used in explosive atmospheres as defined in the scope of IEC 60079-0 or equivalent national standards. If no potentially explosive atmospheres are present or if additional protective measures have been taken: The device may be operated according to the manufacturer's specifications. Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device: Be suitably qualified for their role and the tasks they perform Be trained in explosion protection Be familiar with national regulations For installation, use and maintenance of the device, users must also observe the requirements stated in the Operating Instructions and the standards: GB 50257-2014: "Code for construction and acceptance of electric device for explosion atmospheres and fire hazard electrical equipment installation engineering". GB/T 3836.15-2017: "Explosive atmospheres, Part 13: Equipment repair, overhaul, reclamation and modification". GB/T 3836.16-2017: "Explosive atmospheres, Part 15: Electrical installations design, selection and erection". GB/T 3836.16-2017: "Explosive atmospheres, Part 16: Electrical installations inspection and maintenance". GB/T 3836.16-2017: "Explosive atmospheres, Part 16: Electrical installations inspection and maintenance". GB/T 3836.16-2017: "Explosive atmospheres, Part 16: Electrical installations inspection and maintenance". GB/T 3836.16-2017: "Explosive atmospheres, Part 16: Electrical installations inspection and maintenance". GB/T 3836.16-2017: "Explosive atmospheres, Part 16: Electrical installation gluations. Do not operate the device outside the specified electrical, thermal and mechanical parameters. Don to operate the device in media to which the wetted materials have sufficient durability. Avoid electrostatic charging: Of plastic surfaces (e.g. enclosure, sensor ele

Safety instructions: Special conditions

• To avoid electrostatic charging: Do not rub surfaces with a dry cloth.


• In the event of additional or alternative special varnishing on the enclosure or other metal parts or for adhesive plates:

- Observe the danger of electrostatic charging and discharge.
- Do not install in the vicinity of processes (≤ 0.5 m) generating strong electrostatic charges.

Basic specification, Position 6 = 4


In an explosive atmosphere: Waiting time before opening the electronics compartment after switching off the power supply: 17 minutes.

Safety instructions: Installation



• 1

- A Zone 21
- 1 Tank; Hazardous area Zone 20
- 2 Version
- 3 Temperature separator (optional at 150 ℃)
- 4 Electronic insert; Electronic compartment Ex tb
- 5 Enclosure
- 6 Power supply
- 7 Potential equalization line
- 8 Potential equalization



₽ 2

- A Zone 20, Zone 21
- B Zone 21
- 1 Tank; Hazardous area Zone 20
- 2 Version
- 3 Sensor enclosure
- 4 Temperature separator (optional at 150 °C)
- 5 Electronic insert; Electronic compartment Ex tb
- 6 Electronics enclosure
- 7 Power supply
- 8 Potential equalization line
- 9 Potential equalization
- After mounting and connecting the sensor, ingress protection of the enclosure must be at least IP65.
- Perform the following to achieve the degree of protection IP66/67 or IP66/68:
 - Screw the cover tight.
 - Mount the cable entry correctly.
- Use a process connection seal that meets the materials compatibility and temperature requirements.
- When connecting the cables, ensure there is adequate strain relief at place of installation.

- Protect the connecting cable between the separate enclosure and the level sensor from tension and friction (e.g. due to electrostatic charge from medium flow).
- Observe the maximum process conditions according to the manufacturer's Operating Instructions.
- At high medium temperatures, note flange pressure load capacity as a factor of temperature.
- Max. heat-up of device surface in Zone 20 under fault conditions: <10 K (measured with deposited material with a layer >200 mm in thickness).
- Max. heat-up of device surface in Zone 21 or Zone 22 under fault conditions: <23 K.
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and tank fittings.
- Support extension tube of the device if a dynamic load is expected.
- Only use certified cable entries suitable for the application. Observe national regulations and standards.
- When operating the transmitter enclosure at an ambient temperature under -20 °C, use appropriate cables and cable entries permitted for this application.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection. The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- Continuous service temperature of the connecting cable: -50 °C to \geq +93 °C; in accordance with the range of service temperature taking into account additional influences of the process conditions ($T_{a,min}$), ($T_{a,max}$ +23 K).
- Before operation:
 - Screw in the cover all the way.
 - Tighten the securing clamp on the cover.
- In potentially explosive atmospheres:
 - Do not disconnect the electrical connection of the power supply circuit when energized.
 - Do not open the connection compartment cover and the electronics compartment cover when energized.

Accessory high pressure sliding sleeve

The high pressure sliding sleeve can be used for a continuous setting of the switch point and is suited for zone separation if mounted properly (see Operating Instructions).

Potential equalization

Integrate the device into the local potential equalization.

Temperature tables



Basic specification, Position 8 = 3, 7: T_a restriction to -40 °C

Compact version

Basic specification, Position 7 = A

Device type	Basic specification, Position 11	Permissible process temperature T _p	Maximum surface temperature		Permissible ambient temperature T _a
		FTM50 FTM51	Fork Zone 20	Enclosure Zone 21	Enclosure
FTM50 FTM51	D, E	−50 to +150 °C	T ₂₀₀ 160 ℃	T160 ℃	−50 to +60 °C
FTM50 FTM51	F, H	−50 to +280 °C	Т ₂₀₀ 290 °С	T290 °C	−50 to +60 °C
FTM50 FTM51	Ј, К	−50 to +230 °C	Т ₂₀₀ 240 °С	T240 °C	−50 to +60 °C
FTM50 FTM51	У	−50 to +300 °C	T ₂₀₀ 310 ℃	T310℃	−50 to +60 °C
FTM52		-40 to +80 °C	T ₂₀₀ 90 °C	T83 ℃	-40 to +60 °C

Version with separate enclosure

Basic specification, Position 7 = D, E, G, H (Sensor)

Device type	Basic specification, Position 11	Permissible process temperature T _p	Maximum surface temperature		Permissible ambient temperature T _a
		Fork	Fork Zone 20	Sensor enclosure Zone 20/21	Sensor enclosure
FTM50 FTM51	D, E	−50 to +150 °C	T ₂₀₀ 160 ℃	T160 °C	−50 to +80 °C
FTM50 FTM51	F, H	−50 to +280 °C	T ₂₀₀ 290 ℃	T290 °C	−50 to +80 °C
FTM50 FTM51	Ј, К	−50 to +230 °C	T ₂₀₀ 240 ℃	T240 °C	−50 to +80 °C
FTM50 FTM51	Ү	−50 to +300 °C	T ₂₀₀ 310 ℃	T310 °C	−50 to +80 °C
FTM52		−40 to +80 °C	Т ₂₀₀ 90 °С	T90 °C	-40 to +80 °C

Device type	Maximum surface temperature Electronics enclosure Zone 21	Permissible ambient temperature T _a Electronics enclosure
FTM50 FTM51 FTM52	Τ83 ℃	-50 to +60 ℃

Basic specification, Position 7 = D, E, G, H (Enclosure)

Description notes


1st column: Device type

2nd column: Position 7 or 11

3rd column: Relay current

Column P1 to P5: Position (temperature value) on the axes of the derating

- T_a: Ambient temperature in °C
- T_p: Process temperature in °C



Basic specification, Position 8 = H

with Basic specification, Position 6 = 1

			P1		P2		Р3		P4		P5	
			Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	T _a
FTM50	7 = A	180 mA	-50	60	60	60	150	40	150	-50	-50	-50
FTM51		350 mA	-50	50	60	50	150	30	150	-50	-50	-50
FTM50	11 = D, E	180 mA	-50	60	75	60	150	55	150	-50	-50	-50
FTM51		350 mA	-50	50	80	50	150	45	150	-50	-50	-50
FTM50 FTM51	11 = J, K	180 mA	-50	60	75	60	230	50	230	-50	-50	-50
FIM51		350 mA	-50	50	90	50	230	40	230	-50	-50	-50
FTM50	11 = F, H	180 mA	-50	60	85	60	280	50	280	-50	-50	-50
FTM51		350 mA	-50	50	105	50	280	40	280	-50	-50	-50
FTM50	11 = Y	180 mA	-50	60	85	60	300	50	300	-50	-50	-50
FTM51		350 mA	-50	50	105	50	300	40	300	-50	-50	-50
FTM52		180 mA	-40	60	60	60	80	55	80	-40	-40	-40
		350 mA	-40	50	60	50	80	45	80	-40	-40	-40

		P1		P2		Р3		P4		P5	
		Tp	T _a	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50 FTM51	7 = A	-50	60	80	60	150	45	150	-50	-50	-50
FTM50 FTM51	11 = D, E	-50	60	130	60	150	55	150	-50	-50	-50
FTM50 FTM51	11 = J, K	-50	60	145	60	230	55	230	-50	-50	-50
FTM50 FTM51	11 = F, H	-50	60	175	60	280	55	280	-50	-50	-50
FTM50 FTM51	11 = Y	-50	60	175	60	300	55	300	-50	-50	-50
FTM52		-40	60	80	60	80	60	80	-40	-40	-40

with Basic specification, Position 6 = 4

			P1		P2		P3		P4		P5	
			Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50	7 = A	2 A	-50	60	60	60	150	40	150	-50	-50	-50
FTM51		4 A	-50	50	60	50	150	30	150	-50	-50	-50
		6 A	-50	40	60	40	60	40	60	-50	-50	-50
FTM50	11 = D, E	2 A	-50	60	75	60	150	55	150	-50	-50	-50
FTM51		4 A	-50	50	80	50	150	45	150	-50	-50	-50
		6 A	-50	40	110	40	150	35	150	-50	-50	-50
FTM50	11 = J, K	2 A	-50	60	75	60	230	50	230	-50	-50	-50
FTM51		4 A	-50	50	90	50	230	40	230	-50	-50	-50
		6 A	-50	40	125	40	230	35	230	-50	-50	-50
FTM50	11 = F, H	2 A	-50	60	85	60	280	50	280	-50	-50	-50
FTM51		4 A	-50	50	105	50	280	40	280	-50	-50	-50
		6 A	-50	40	155	40	280	35	280	-50	-50	-50
FTM50	11 = Y	2 A	-50	60	85	60	300	50	300	-50	-50	-50
FTM51		4 A	-50	50	105	50	300	40	300	-50	-50	-50
		6 A	-50	40	155	40	300	35	300	-50	-50	-50
FTM52		2 A	-40	60	60	60	80	55	80	-40	-40	-40
		4 A	-40	50	60	50	80	45	80	-40	-40	-40
		6 A	-40	45	65	45	80	35	50	-40	-40	-40

		P1	P1			P3		P4		P5	
		Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50 FTM51	7 = A	-50	60	75	60	150	40	150	-50	-50	-50
FTM50 FTM51	11 = D, E	-50	60	110	60	150	55	150	-50	-50	-50
FTM50 FTM51	11 = J, K	-50	60	125	60	230	55	230	-50	-50	-50
FTM50 FTM51	11 = F, H	-50	60	145	60	280	55	280	-50	-50	-50
FTM50 FTM51	11 = Y	-50	60	145	60	300	55	300	-50	-50	-50
FTM52		-40	60	75	60	80	55	80	-40	-40	-40

Basic specification, Position 8 = 3, 5, 6

with Basic specification, Position 6 = 1

			P1		P2		Р3		P4		P5	
			Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50	7 = A	180 mA	-50	60	60	60	150	25	150	-50	-50	-50
FTM51		350 mA	-50	50	55	50	85	40	85	-50	-50	-50
FTM50	11 = D, E	180 mA	-50	60	70	60	150	50	150	-50	-50	-50
FTM51		350 mA	-50	50	75	50	150	40	150	-50	-50	-50
	11 = J, K	180 mA	-50	60	75	60	230	50	230	-50	-50	-50
FTM51		350 mA	-50	50	85	50	230	40	230	-50	-50	-50
FTM50	11 = F, H	180 mA	-50	60	80	60	280	50	280	-50	-50	-50
FTM51		350 mA	-50	50	95	50	280	40	280	-50	-50	-50
FTM50	11 = Y	180 mA	-50	60	80	60	300	50	300	-50	-50	-50
FTM51		350 mA	-50	50	95	50	300	40	300	-50	-50	-50
FTM52		180 mA	-40	60	60	60	80	50	80	-40	-40	-40
		350 mA	-40	50	55	50	80	40	80	-40	-40	-40

		P1		P2		Р3		P4		P5	
		Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50 FTM51	7 = A	-50	60	70	60	150	30	150	-50	-50	-50
FTM50 FTM51	11 = D, E	-50	60	115	60	150	55	150	-50	-50	-50
FTM50 FTM51	11 = J, K	-50	60	135	60	230	55	230	-50	-50	-50
FTM50 FTM51	11 = F, H	-50	60	155	60	280	50	280	-50	-50	-50
FTM50 FTM51	11 = Y	-50	60	155	60	300	50	300	-50	-50	-50
FTM52		-40	60	70	60	80	55	80	-40	-40	-40

with Basic specification, Position 6 = 4

			P1		P2		P3		P4		P5	
			Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50	7 = A	2 A	-50	50	50	50	75	40	75	-50	-50	-50
FTM51		4 A	-50	45	55	45	65	40	65	-50	-50	-50
		6 A	-50	40	50	40	50	40	50	-50	-50	-50
FTM50	11 = D, E	2 A	-50	50	60	40	150	40	150	-50	-50	-50
FTM51		4 A	-50	45	90	45	150	40	150	-50	-50	-50
		6 A	-50	40	85	40	150	30	150	-50	-50	-50
FTM50	11 = J, K	2 A	-50	50	65	50	230	40	230	-50	-50	-50
FTM51		4 A	-50	45	110	45	230	35	230	-50	-50	-50
		6 A	-50	40	105	40	230	30	230	-50	-50	-50
FTM50	11 = F, H	2 A	-50	50	75	50	280	40	280	-50	-50	-50
FTM51		4 A	-50	45	140	45	280	35	280	-50	-50	-50
		6 A	-50	40	135	40	280	30	280	-50	-50	-50
FTM50	11 = Y	2 A	-50	50	75	50	300	40	300	-50	-50	-50
FTM51		4 A	-50	45	140	45	300	35	300	-50	-50	-50
		6 A	-50	40	135	40	300	30	300	-50	-50	-50
FTM52		2 A	-40	50	50	50	80	35	80	-40	-40	-40
		4 A	-40	45	50	45	80	35	80	-40	-40	-40
		6 A	-40	40	50	40	50	40	50	-40	-40	-40

		P1	P1			P3		P4		P5	
		Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50 FTM51	7 = A	-50	60	70	60	150	30	150	-50	-50	-50
FTM50 FTM51	11 = D, E	-50	60	100	60	150	55	150	-50	-50	-50
FTM50 FTM51	11 = J, K	-50	60	115	60	230	50	230	-50	-50	-50
FTM50 FTM51	11 = F, H	-50	60	130	60	280	50	280	-50	-50	-50
FTM50 FTM51	11 = Y	-50	60	130	60	300	50	300	-50	-50	-50
FTM52		-40	60	70	60	80	55	80	-40	-40	-40

Basic specification, Position 8 = 7

with Basic specification, Position 6 = 1

			P1		P2		Р3		P4		P5	
			Tp	T _a	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50	7 = A	180 mA	-50	60	60	60	150	25	150	-50	-50	-50
FTM51		350 mA	-50	50	55	50	85	40	85	-50	-50	-50
FTM50	11 = D, E	180 mA	-50	60	75	60	150	50	150	-50	-50	-50
FTM51		350 mA	-50	50	75	50	150	40	150	-50	-50	-50
	11 = J, K	180 mA	-50	60	75	60	230	50	230	-50	-50	-50
FTM51		350 mA	-50	50	85	50	230	40	230	-50	-50	-50
FTM50	11 = F, H	180 mA	-50	60	80	60	280	50	280	-50	-50	-50
FTM51		350 mA	-50	50	95	50	280	40	280	-50	-50	-50
FTM50	11 = Y	180 mA	-50	60	80	60	300	50	300	-50	-50	-50
FTM51		350 mA	-50	50	95	50	300	40	300	-50	-50	-50
FTM52		180 mA	-40	60	60	60	80	50	80	-40	-40	-40
		350 mA	-40	50	55	50	80	40	80	-40	-40	-40

		P1		P2		Р3		P4		P5	
		Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50 FTM51	7 = A	-50	60	70	60	150	30	150	-50	-50	-50
FTM50 FTM51	11 = D, E	-50	60	115	60	150	55	150	-50	-50	-50
FTM50 FTM51	11 = J, K	-50	60	135	60	230	55	230	-50	-50	-50
FTM50 FTM51	11 = F, H	-50	60	155	60	280	50	280	-50	-50	-50
FTM50 FTM51	11 = Y	-50	60	155	60	300	50	300	-50	-50	-50
FTM52		-40	60	70	60	80	55	80	-40	-40	-40

			P1		P2		P3		P4		P5	
			Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50	7 = A	2 A	-50	45	50	45	100	20	100	-50	-50	-50
FTM51		4 A	-50	35	35	35	70	20	70	-50	-50	-50
FTM50	11 = D, E	2 A	-50	45	50	45	150	35	150	-50	-50	-50
FTM51		4 A	-50	35	35	35	150	25	150	-50	-50	-50
FTM50 FTM51	11 = J, K	2 A	-50	45	50	45	230	35	230	-50	-50	-50
FIM51		4 A	-50	35	40	35	230	20	230	-50	-50	-50
FTM50	11 = F, H	2 A	-50	45	50	45	280	35	280	-50	-50	-50
FTM51		4 A	-50	35	40	35	280	20	280	-50	-50	-50
FTM50	11 = Y	2 A	-50	45	50	45	300	35	300	-50	-50	-50
FTM51		4 A	-50	35	40	35	300	20	300	-50	-50	-50
FTM52		2 A	-40	45	50	45	80	35	80	-40	-40	-40
		4 A	-40	35	35	35	70	20	70	-40	-40	-40

with Basic specification, Position 6 = 4

		P1		P2		P3		P4		P5	
		Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50 FTM51	7 = A	-50	60	70	60	150	30	150	-50	-50	-50
FTM50 FTM51	11 = D, E	-50	60	100	60	150	55	150	-50	-50	-50
FTM50 FTM51	11 = J, K	-50	60	115	60	230	50	230	-50	-50	-50
FTM50 FTM51	11 = F, H	-50	60	130	60	280	50	280	-50	-50	-50
FTM50 FTM51	11 = Y	-50	60	130	60	300	50	300	-50	-50	-50
FTM52		-40	60	70	60	80	55	80	-40	-40	-40

Device type	Surface temperature T_{200}	Ambient temperature T _a (ambient): probe with Basic specification, Position 7 = D, E, G, H
FTM50 FTM51	T 130 °C	max. 80 °C
FTM52		max. 80 °C

Deposited material with a layer of 200 mm

Device type	Basic specification, Position	P1		P2		Р3		P4		P5	
		Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta	Tp	Ta
FTM50 FTM51	7 = A	-50	40	40	40	40	40	40	-50	-50	-50
FTM50 FTM51	11 = D, E, J, K, F, H, Y	-50	40	40	40	40	40	40	-50	-50	-50
FTM52		-40	40	40	40	40	40	40	-40	-40	-40

Connection data

Basic specification, Position 6	Power supply	Output				
1	19 to 253 $V_{AC},$ 50/60 Hz, max. 1.0 W $U_m = 253 \; V_{AC}$	max. 350 mA				
2	10 to 55 V_{DC} max. 0.86 W U_{m} = 253 V_{AC}	PNP transistor, max. 350 mA				
4	19 to 55 V _{DC} , max. 1.5 W 19 to 253 V _{AC} , 50/60 Hz, max. 1.5 W U _m = 253 V _{AC}	$\begin{array}{l} 2 \text{ potential free change-over} \\ \text{contacts,} \\ 253 \ V_{AC}, \ 4 \ A; \\ 1 \ 500 \ VA \ / \ \cos \phi = 1; \ 750 \ VA \\ \cos \phi > 0.7 \\ 30 \ V_{DC}, \ 4 \ A; \ 125 \ V_{DC}, \ 0.2 \ A \end{array}$				
5	11 to 35 V _{DC} , 8/16 mA, max. 0.6 W $U_m = 253 V_{AC}$	<3.6 mA / 8 mA / 16 mA				



71568471

www.addresses.endress.com

