

Safety Instructions

Levelflex

FMP50/51/52/53/54/55/56/57

4-20 mA HART, 4-wire

Ex d [ia] IIC T6-T1 Ga/Gb
DIP A20/21 T_A, T* IP6X



Document: XA01330F-B
Safety instructions for electrical apparatus for explosion-hazardous areas

Levelflex

FMP50/51/52/53/54/55/56/57

4-20 mA HART

Table of Contents

Associated documentation	4
Supplementary documentation	4
Manufacturer's certificates	4
Extended order code	4
Safety instructions: General	6
Safety instructions: Special conditions	6
Safety instructions: Installation	7
Safety instructions: Zone 0	8
Temperature tables	8
Connection data	8

Associated documentation	This document is an integral part of the following Operating Instructions: BA01000F/00 (FMP50), BA01001F/00 (FMP51/52/54), BA01002F/00 (FMP53), BA01003F/00 (FMP55), BA01004F/00 (FMP56/57) The Operating Instructions pertaining to the device apply.															
Supplementary documentation	Explosion-protection brochure: CP00021Z/11 The Explosion-protection brochure is available: ■ In the download area of the Endress+Hauser website: www.endress.com → Download → Advanced → Documentation Code: CP00021Z ■ On the CD for devices with CD-based documentation															
Manufacturer's certificates	NEPSI Declaration of Conformity Certificate number: GYJ11.1553X Affixing the certificate number certifies conformity with the standards: ■ GB3836.1-2010 ■ GB3836.2-2010 ■ GB3836.4-2010 ■ GB3836.20-2010 ■ GB12476.1-2000 ■ GB12476.4-2010, with the following standard: – IEC 61241-0:2004															
Extended order code	The extended order code is indicated on the nameplate, which is affixed to the device in such a way that it is clearly visible. Additional information about the nameplate is provided in the associated Operating Instructions.															
Structure of the extended order code																
<table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: right; padding-right: 10px;">FMP5x</td> <td style="padding: 0 10px;">-</td> <td style="text-align: left; padding-left: 10px;">*****</td> <td style="padding: 0 10px;">+</td> <td style="text-align: left; padding-left: 10px;">A*B*C*D*E*F*G*..</td> </tr> <tr> <td style="text-align: right; padding-right: 10px;">-----</td> <td style="padding: 0 10px;">-----</td> <td style="text-align: left; padding-left: 10px;">-----</td> <td style="padding: 0 10px;">-----</td> <td></td> </tr> <tr> <td style="text-align: right; padding-right: 10px;">Device type</td> <td style="padding: 0 10px;">Basic specifications</td> <td style="text-align: left; padding-left: 10px;">Optional specifications</td> <td></td> <td></td> </tr> </table>		FMP5x	-	*****	+	A*B*C*D*E*F*G*..	-----	-----	-----	-----		Device type	Basic specifications	Optional specifications		
FMP5x	-	*****	+	A*B*C*D*E*F*G*..												
-----	-----	-----	-----													
Device type	Basic specifications	Optional specifications														
<p>* = Placeholder At this position, an option (number or letter) selected from the specification is displayed instead of the placeholders.</p>																
<ul style="list-style-type: none"> ■ Basic specifications The features that are absolutely essential for the device (mandatory features) are specified in the basic specifications. The number of positions depends on the number of features available. The selected option of a feature can consist of several positions. ■ Optional specifications The optional specifications describe additional features for the device (optional features). The number of positions depends on the number of features available. The features have a 2-digit structure to aid identification (e.g. JA). The first digit (ID) stands for the feature group and consists of a number or a letter (e.g. J = test, certificate). The second digit constitutes the value that stands for the feature within the group (e.g. A = 3.1 material (wetted parts), inspection certificate). 																
<p>More detailed information about the device is provided in the following tables. These tables describe the individual positions and IDs in the extended order code which are relevant to hazardous locations.</p>																

Device type: FMP50, FMP51, FMP52, FMP53, FMP54, FMP55, FMP56, FMP57

Basic specifications

Position	Selected option		Description
1, 2 Approval	FMP5x	N3 *1	Ex d [ia] IIC T6-T1 Ga/Gb, DIP A20/21 T _A , T* IP6X
3 Power Supply; Output	FMP5x	K L	4-wire 90...253 VAC, 4-20 mA HART 4-wire 10,4...48 VDC, 4-20 mA HART
4 Display; Operation	FMP5x	A C E L M	Without, via communication SD02, 4-line, push buttons + data backup function SD03, 4-line, illum., touch control + data backup function Prepared for display FHX50 + M12 connection Prepared for display FHX50 + custom connection
5 Housing	FMP51/52/54-57	B	GT18 dual compartment, 316L
	FMP5x	C	GT20 dual compartment, Alu coated
9, 10 Seal	FMP50	A1	Viton, -20...80 °C
	FMP51	A4 B3 C3 E1	Viton, -30...150 °C EPDM, -40...120 °C Kalrez, -20...200 °C FVMQ, -40...150 °C
	FMP53	AD B5 C4	FKM, FDA, USP Cl. VI, -10..150 °C EPDM, FDA, USP Cl. VI, -20..130 °C Kalrez, FDA, USP Cl. VI, -20..150 °C
	FMP54	D1 D2	Graphite, -196...280 °C (XT) Graphite, -196...450 °C (HT)
	FMP56	AB B3	Viton, -30...120 °C EPDM, -40...120 °C
	FMP57	A4 B3 C5	Viton, -30...150 °C EPDM, -40...120 °C Kalrez, -5...185 °C

*1 The designation changes in connection with "Display; Operation" = "L" or "M":
Ex d [ia] IIC T6-T1 Ga/Gb, Ex ta [ia Da] IIIC Txx°C Da/Db

Optional specifications

ID	Selected option		Description
Mx Probe Design	FMP5x	MB	Sensor remote, 3 m/9 ft cable, detachable + mounting bracket
	FMP53	MA	Sensor compact, detachable
	FMP50-54/56/57	MC MD	Sensor remote, 6 m/18 ft cable, detachable + mounting bracket Sensor remote, 9 m/27 ft cable, detachable + mounting bracket
Nx Accessory Mounted	FMP51/52/55	NC	Gas-tight feed through

**Safety instructions:
General**

- Staff must meet the following conditions for mounting, electrical installation, commissioning and maintenance of the device:
 - Be suitably qualified for their role and the tasks they perform
 - Be trained in explosion protection
 - Be familiar with national regulations
- For installation, use and maintenance of the device, users must also observe the requirements stated in the Operating Instructions and the standards:
 - GB50257-1996: "Code for construction and acceptance of electric device for explosion atmospheres and fire hazard electrical equipment installation engineering".
 - GB3836.13-1997: "Electrical apparatus for explosive gas atmospheres, Part 13: Repair and overhaul for apparatus used in explosive gas atmospheres".
 - GB3836.15-2000: "Electrical apparatus for explosive gas atmospheres, Part 15: Electrical installations in hazardous area (other than mines)".
 - GB3836.16-2006: "Electrical apparatus for explosive gas atmospheres, Part 16: Inspection and maintenance of electrical installation (other than mines)".
 - GB15577-2007: "Safety regulations for dust explosive prevention and protection".
 - GB12476.2-2006: "Electrical apparatus for use in the presence of combustible dust, Part 1-2: Electrical apparatus protected by enclosures and surface temperature limitation - Selection, installation and maintenance". (Only if installed in dust hazardous areas).
- Install the device according to the manufacturer's instructions and national regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- Only use the device in media to which the wetted materials have sufficient durability.
- Avoid electrostatic charging:
 - Of plastic surfaces (e.g. housing, sensor element, special varnishing , attached additional plates, ..)
 - Of isolated capacities (e.g. isolated metallic plates)
- Refer to the temperature tables for the relationship between the permitted ambient temperature for the sensor and/or transmitter, depending on the range of application, and the temperature class.
- Modifications to the device can affect the explosion protection and must be carried out by staff authorized to perform such work by Endress+Hauser.
- When replacing the probe electronics or opening the connection between the remote cable and the probe, a jumper plug must be used or a short-circuit must be established between the probe contact and the potential equalization conductor to avoid electrostatically charging the probe.
- After mounting and connecting the probe, ingress protection of the housing must be at least IP65. Perform the following to achieve the degree of protection:
 - Screw the cover tight.
 - Mount the cable entry correctly.
- When using in hybrid mixtures (gas and dust occurring simultaneously), observe additional measures for explosion protection.


**Safety instructions:
Special conditions**

Permitted ambient temperature range at the electronics housing: $-40^{\circ}\text{C} \leq T_a \leq +80^{\circ}\text{C}$.
Observe the information in the temperature tables.

Device type FMP52, FMP55

- A probe coated with non-conductive material can be used if avoiding electrostatic charging (e.g. through friction, cleaning, maintenance, strong medium flow).
- In the case of process connections made of polymeric material or with polymeric coatings, avoid electrostatic charging of the plastic surfaces.
- In the event of additional or alternative special varnishing on the housing or other metal parts:
 - Observe the danger of electrostatic charging and discharge.
 - Do not rub surfaces with a dry cloth.

Safety instructions:
Installation



↗ 1

A Zone 1, Zone 21

- 1 Tank; Zone 0, Zone 1 or Zone 20, Zone 21
- 2 Electronics compartment Ex ia; Electronic insert
- 3 Connection compartment Ex d
- 4 Power supply
- 5 Potential equalization line
- 6 Potential equalization

- After aligning (rotating) the housing, retighten the fixing screw (see Operating Instructions).
- When mounting the device:
 - Exclude any mechanical damage or friction during the application.
 - Pay particular attention to flow conditions and tank fittings.
- Continuous service temperature of the connecting cable: $-40 \text{ to } +85^\circ\text{C}$; in accordance with the range of service temperature taking into account additional influences of the process conditions ($T_{a,\min}$), ($T_{a,\max} +20 \text{ K}$).
- In potentially explosive atmospheres:
 - Do not open the electrical connection of the power supply circuit when energized.
 - Do not open the connection compartment cover.
- Only use certified cable entries suitable for the application.
Observe national regulations or standards. Accordingly, the connection terminal does not include any ignition sources.
- When operating the transmitter housing at an ambient temperature under -20°C , use appropriate cables and cable entries permitted for this application.
- When connecting through a conduit entry approved for this purpose, mount the associated sealing unit directly at the housing.
- Only use certified cable entries or sealing plugs.
The metal sealing plugs supplied meet this requirement.
- Seal unused entry glands with approved sealing plugs that correspond to the type of protection.
The plastic transport sealing plug does not meet this requirement and must therefore be replaced during installation.
- Before operation:
 - Screw in the cover all the way.
 - Tighten the securing clamp on the cover.

Basic specification, Position 3 (Power Supply; Output) = K

- Connect the protective ground to the device.

Intrinsic safety

- The device can be connected to the Endress+Hauser FXA291 service tool: refer to the Operating Instructions.

Potential equalization

- Integrate the device into the local potential equalization.

**Safety instructions:
Zone 0**

- In the event of potentially explosive vapor/air mixtures, only operate the device under atmospheric conditions.
 - Temperature: -20 to +60 °C
 - Pressure: 80 to 110 kPa (0.8 to 1.1 bar)
 - Air with normal oxygen content, usually 21 % (V/V)
- If no potentially explosive mixtures are present, or if additional protective measures have been taken, the device may also be operated under non-atmospheric conditions in accordance with the manufacturer's specifications.

Temperature tables

→ 9

Connection data

Basic specification, Position 1, 2 (Approval) = N3

Connection compartment Ex d

Basic specification, Position 3 (Power Supply; Output) = K (TRC [09])

Terminal 1 (L), 2 (N)	Terminal 3 (+), 4 (-)
Power supply: $U_N = 253 \text{ V AC}$; 50/60 Hz $U_m = 250 \text{ V}$ $I_N = 25 \text{ mA}$ $I_{\max} = 160 \text{ mA}$	Output 4...20 mA: $U_N = 22 \text{ V DC}$ $U_m = 250 \text{ V}$ $I_{\max} = 22 \text{ mA}$

Basic specification, Position 3 (Power Supply; Output) = L (TRC [08])

Terminal 1 (L+), 2 (L-)	Terminal 3 (+), 4 (-)
Power supply: $U_N = 48 \text{ V DC}$ $U_m = 250 \text{ V}$ $I_N = 112 \text{ mA}$ $I_{\max} = 300 \text{ mA}$	Output 4...20 mA: $U_N = 22 \text{ V DC}$ $U_m = 250 \text{ V}$ $I_{\max} = 22 \text{ mA}$

Electronics compartment Ex i**Service interface (CDI)**

Taking the following values into consideration, the device can be connected to the certified Endress+Hauser FXA291 service tool or a similar interface:

Service interface																								
$U_i = 7.3 \text{ V}$																								
effective inner inductance $L_i = \text{negligible}$ effective inner capacitance $C_i = \text{negligible}$																								
$U_o = 7.3 \text{ V}$ $I_o = 100 \text{ mA}$ $P_o = 160 \text{ mW}$ $L_o (\text{mH}) =$ <table border="1" style="display: inline-table; vertical-align: middle;"><tr><td>5.00</td><td>2.00</td><td>1.00</td><td>0.50</td><td>0.20</td><td>0.10</td><td>0.05</td><td>0.02</td><td>0.01</td><td>0.005</td><td>0.002</td><td>0.001</td></tr><tr><td>0.73</td><td>1.20</td><td>1.60</td><td>2.00</td><td>2.60</td><td>3.20</td><td>4.00</td><td>5.50</td><td>7.30</td><td>10.00</td><td>12.70</td><td>12.70</td></tr></table>	5.00	2.00	1.00	0.50	0.20	0.10	0.05	0.02	0.01	0.005	0.002	0.001	0.73	1.20	1.60	2.00	2.60	3.20	4.00	5.50	7.30	10.00	12.70	12.70
5.00	2.00	1.00	0.50	0.20	0.10	0.05	0.02	0.01	0.005	0.002	0.001													
0.73	1.20	1.60	2.00	2.60	3.20	4.00	5.50	7.30	10.00	12.70	12.70													

Temperature tables

Table of Contents

General notes	10
Diagram	10
Probe design: compact	
Probe and electronics housing: Zone 1	
FMP50	11
FMP51	11
FMP52	12
FMP53	12
FMP54, Position 9, 10 (Seal) = D1	13
FMP54, Position 9, 10 (Seal) = D2	14
FMP55	15
FMP56	15
FMP57	16
Probe: Zone 0, Electronics housing: Zone 1	
FMP5x	16
Probe: Zone 20, Zone 21, Electronics housing: Zone 21	
FMP5x	17
Probe design: remote	
Probe: Zone 0, Zone 1, Electronics housing: Zone 1	
FMP5x	17

General notes

Unless otherwise indicated, the positions always refer to the basic specification.

Note!


Observe the permitted temperature range at the probe.

*1 = Functional
Max. permissible process temperature

Selection table

Position 1, 2 (Approval)		Position 5 (Housing)	
N3	Ex d [ia] IIC T6-T1 Ga/Gb, DIP A20/21 T _A , T* IP6X	B	GT18 dual compartment, 316L
		C	GT20 dual compartment, Alu coated

Position 3 (Power Supply; Output)		Transmission code of the terminal module
K	4-wire 90...253 VAC, 4-20 mA HART	TRC [09]
L	4-wire 10,4...48 VDC, 4-20 mA HART	TRC [08]

Diagram**Example diagrams to the temperature tables**

2

A Version 1
B Version 2

T_a Ambient temperature
 T_p Process temperature

Probe design: compact**Probe and electronics housing: Zone 1****FMP50****Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Position 5 (Housing) = C												
Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-20 °C	60 °C	60 °C	60 °C	80 °C	55 °C	80 °C	-20 °C	-20 °C	-20 °C	-20 °C	-

FMP51**Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Position 5 (Housing) = B												
Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-40 °C	60 °C	60 °C	60 °C	85 °C	51 °C	85 °C	-40 °C	-40 °C	-40 °C	-40 °C	-
T5 (100 °C)	-40 °C	75 °C	75 °C	75 °C	100 °C	66 °C	100 °C	-40 °C	-40 °C	-40 °C	-40 °C	-
T4 (135 °C)	-40 °C	76 °C	76 °C	76 °C	135 °C	62 °C	135 °C	-40 °C	-40 °C	-40 °C	-40 °C	-
T3 (200 °C)	-40 °C	76 °C	76 °C	76 °C	200 °C	46 °C	200 °C	-40 °C	-40 °C	-40 °C	-40 °C	-

Position 5 (Housing) = C												
Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-40 °C	60 °C	60 °C	60 °C	85 °C	53 °C	85 °C	-40 °C	-40 °C	-40 °C	-40 °C	-
T5 (100 °C)	-40 °C	75 °C	75 °C	75 °C	100 °C	68 °C	100 °C	-40 °C	-40 °C	-40 °C	-40 °C	-
T4 (135 °C)	-40 °C	76 °C	76 °C	76 °C	135 °C	64 °C	135 °C	-40 °C	-40 °C	-40 °C	-40 °C	-
T3 (200 °C)	-40 °C	76 °C	76 °C	76 °C	200 °C	51 °C	200 °C	-40 °C	-40 °C	-40 °C	-40 °C	-

Probe and electronics housing: Zone 1**FMP52****Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-50 °C	60 °C	60 °C	60 °C	85 °C	52 °C	85 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T5 (100 °C)	-50 °C	75 °C	75 °C	75 °C	100 °C	67 °C	100 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T4 (135 °C)	-50 °C	76 °C	76 °C	76 °C	135 °C	63 °C	135 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T3 (200 °C)	-50 °C	76 °C	76 °C	76 °C	200 °C	48 °C	200 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C

Position 5 (Housing) = C												
Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-50 °C	60 °C	60 °C	60 °C	85 °C	54 °C	85 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T5 (100 °C)	-50 °C	75 °C	75 °C	75 °C	100 °C	69 °C	100 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T4 (135 °C)	-50 °C	76 °C	76 °C	76 °C	135 °C	65 °C	135 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T3 (200 °C)	-50 °C	76 °C	76 °C	76 °C	200 °C	53 °C	200 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C

FMP53**Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-20 °C	60 °C	60 °C	60 °C	85 °C	54 °C	85 °C	-20 °C	-20 °C	-20 °C	-	-
T5 (100 °C)	-20 °C	75 °C	75 °C	75 °C	100 °C	69 °C	100 °C	-20 °C	-20 °C	-20 °C	-	-
T4 (135 °C)	-20 °C	76 °C	76 °C	76 °C	135 °C	64 °C	135 °C	-20 °C	-20 °C	-20 °C	-	-
T3 (200 °C)	-20 °C	76 °C	76 °C	76 °C	150 °C	61 °C	150 °C	-20 °C	-20 °C	-20 °C	-	-

Probe and electronics housing: Zone 1

FMP54, Position 9, 10 (Seal) = D1

Position 3 (Power Supply; Output) = K, L (TRC [09/08])

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-196 °C	60 °C	60 °C	60 °C	85 °C	56 °C	85 °C	-40 °C	-40 °C	-40 °C	-196 °C	-16 °C
T5 (100 °C)	-196 °C	75 °C	75 °C	75 °C	100 °C	71 °C	100 °C	-40 °C	-40 °C	-40 °C	-196 °C	-16 °C
T4 (135 °C)	-196 °C	76 °C	76 °C	76 °C	135 °C	68 °C	135 °C	-40 °C	-40 °C	-40 °C	-196 °C	-16 °C
T3 (200 °C)	-196 °C	76 °C	76 °C	76 °C	200 °C	60 °C	200 °C	-40 °C	-40 °C	-40 °C	-196 °C	-16 °C
T2 (300 °C)	-196 °C	76 °C	76 °C	76 °C	280 °C	49 °C	280 °C	-40 °C	-40 °C	-40 °C	-196 °C	-16 °C

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-196 °C	60 °C	60 °C	60 °C	85 °C	57 °C	85 °C	-40 °C	-40 °C	-40 °C	-196 °C	-23 °C
T5 (100 °C)	-196 °C	75 °C	75 °C	75 °C	100 °C	72 °C	100 °C	-40 °C	-40 °C	-40 °C	-196 °C	-23 °C
T4 (135 °C)	-196 °C	76 °C	76 °C	76 °C	135 °C	70 °C	135 °C	-40 °C	-40 °C	-40 °C	-196 °C	-23 °C
T3 (200 °C)	-196 °C	76 °C	76 °C	76 °C	200 °C	64 °C	200 °C	-40 °C	-40 °C	-40 °C	-196 °C	-23 °C
T2 (300 °C)	-196 °C	76 °C	76 °C	76 °C	280 °C	56 °C	280 °C	-40 °C	-40 °C	-40 °C	-196 °C	-23 °C

Probe and electronics housing: Zone 1**FMP54**, Position 9, 10 (Seal) = D2**Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Position 5 (Housing) = B

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (-85 °C)	-196 °C	60 °C	60 °C	60 °C	85 °C	57 °C	85 °C	-40 °C	-40 °C	-40 °C	-196 °C	-26 °C
T5 (100 °C)	-196 °C	75 °C	75 °C	75 °C	100 °C	72 °C	100 °C	-40 °C	-40 °C	-40 °C	-196 °C	-26 °C
T4 (135 °C)	-196 °C	76 °C	76 °C	76 °C	135 °C	72 °C	135 °C	-40 °C	-40 °C	-40 °C	-196 °C	-26 °C
T3 (200 °C)	-196 °C	76 °C	76 °C	76 °C	200 °C	67 °C	200 °C	-40 °C	-40 °C	-40 °C	-196 °C	-26 °C
T2 (300 °C)	-196 °C	76 °C	76 °C	76 °C	300 °C	59 °C	300 °C	-40 °C	-40 °C	-40 °C	-196 °C	-26 °C
T1 (450 °C) *1	-196 °C	76 °C	76 °C	76 °C	450 °C	48 °C	450 °C	-40 °C	-40 °C	-40 °C	-196 °C	-26 °C

Position 5 (Housing) = C

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (-85 °C)	-196 °C	60 °C	60 °C	60 °C	85 °C	58 °C	85 °C	-40 °C	-40 °C	-40 °C	-196 °C	-27 °C
T5 (100 °C)	-196 °C	75 °C	75 °C	75 °C	100 °C	73 °C	100 °C	-40 °C	-40 °C	-40 °C	-196 °C	-27 °C
T4 (135 °C)	-196 °C	76 °C	76 °C	76 °C	135 °C	72 °C	135 °C	-40 °C	-40 °C	-40 °C	-196 °C	-27 °C
T3 (200 °C)	-196 °C	76 °C	76 °C	76 °C	200 °C	67 °C	200 °C	-40 °C	-40 °C	-40 °C	-196 °C	-27 °C
T2 (300 °C)	-196 °C	76 °C	76 °C	76 °C	300 °C	60 °C	300 °C	-40 °C	-40 °C	-40 °C	-196 °C	-27 °C
T1 (450 °C) *1	-196 °C	76 °C	76 °C	76 °C	450 °C	50 °C	450 °C	-40 °C	-40 °C	-40 °C	-196 °C	-27 °C

Probe and electronics housing: Zone 1

FMP55

Position 3 (Power Supply; Output) = K, L (TRC [09/08])

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-50 °C	60 °C	60 °C	60 °C	85 °C	52 °C	85 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T5 (100 °C)	-50 °C	75 °C	75 °C	75 °C	100 °C	67 °C	100 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T4 (135 °C)	-50 °C	76 °C	76 °C	76 °C	135 °C	63 °C	135 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T3 (200 °C)	-50 °C	76 °C	76 °C	76 °C	200 °C	48 °C	200 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-50 °C	60 °C	60 °C	60 °C	85 °C	54 °C	85 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T5 (100 °C)	-50 °C	75 °C	75 °C	75 °C	100 °C	69 °C	100 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T4 (135 °C)	-50 °C	76 °C	76 °C	76 °C	135 °C	64 °C	135 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C
T3 (200 °C)	-50 °C	76 °C	76 °C	76 °C	200 °C	52 °C	200 °C	-40 °C	-40 °C	-40 °C	-50 °C	-37 °C

FMP56

Position 3 (Power Supply; Output) = K, L (TRC [09/08])

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-40 °C	60 °C	60 °C	60 °C	85 °C	51 °C	85 °C	-40 °C	-40 °C	-40 °C	-	-
T5 (100 °C)	-40 °C	75 °C	75 °C	75 °C	100 °C	66 °C	100 °C	-40 °C	-40 °C	-40 °C	-	-
T4 (135 °C)	-40 °C	76 °C	76 °C	76 °C	120 °C	66 °C	120 °C	-40 °C	-40 °C	-40 °C	-	-

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-40 °C	60 °C	60 °C	60 °C	85 °C	54 °C	85 °C	-40 °C	-40 °C	-40 °C	-	-
T5 (100 °C)	-40 °C	75 °C	75 °C	75 °C	100 °C	69 °C	100 °C	-40 °C	-40 °C	-40 °C	-	-
T4 (135 °C)	-40 °C	76 °C	76 °C	76 °C	120 °C	67 °C	120 °C	-40 °C	-40 °C	-40 °C	-	-

Probe and electronics housing: Zone 1**FMP57****Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Position 5 (Housing) = B												
Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-40 °C	60 °C	60 °C	60 °C	85 °C	53 °C	85 °C	-40 °C	-40 °C	-40 °C	-	-
T5 (100 °C)	-40 °C	75 °C	75 °C	75 °C	100 °C	68 °C	100 °C	-40 °C	-40 °C	-40 °C	-	-
T4 (135 °C)	-40 °C	76 °C	76 °C	76 °C	135 °C	64 °C	135 °C	-40 °C	-40 °C	-40 °C	-	-
T3 (200 °C)	-40 °C	76 °C	76 °C	76 °C	185 °C	55 °C	185 °C	-40 °C	-40 °C	-40 °C	-	-

Position 5 (Housing) = C												
Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a										
T6 (85 °C)	-40 °C	60 °C	60 °C	60 °C	85 °C	55 °C	85 °C	-40 °C	-40 °C	-40 °C	-	-
T5 (100 °C)	-40 °C	75 °C	75 °C	75 °C	100 °C	70 °C	100 °C	-40 °C	-40 °C	-40 °C	-	-
T4 (135 °C)	-40 °C	76 °C	76 °C	76 °C	135 °C	66 °C	135 °C	-40 °C	-40 °C	-40 °C	-	-
T3 (200 °C)	-40 °C	76 °C	76 °C	76 °C	185 °C	59 °C	185 °C	-40 °C	-40 °C	-40 °C	-	-

Probe: Zone 0, Electronics housing: Zone 1**FMP5x****Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Position 5 (Housing) = B, C												
Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T _p	T _a ^{*2}	T _p	T _a ^{*2}	T _p	T _a						
T6 (85 °C)	-20 °C	60 °C	60 °C	60 °C	60 °C	60 °C	60 °C	60 °C	-40 °C	-20 °C	-40 °C	-

*2 FMP50, FMP53
without remote sensor = -20 °C

Probe: Zone 20, Zone 21, Electronics housing: Zone 21**FMP5x****Position 3 (Power Supply; Output) = K (TRC [09])**

Position 5 (Housing) = B, C
-
$T = T_a + 9 \text{ K}$

Position 3 (Power Supply; Output) = L (TRC [08])

Position 5 (Housing) = B, C
-
$T = T_a + 8 \text{ K}$

Probe design: remote**Probe: Zone 0, Zone 1, Electronics housing: Zone 1****FMP5x, Optional specification, ID Mx (Probe Design) = MB, MC, MD****Position 3 (Power Supply; Output) = K, L (TRC [09/08])**

Temperature class	P 1		P 2		P 3		P 4		P 5		P 6	
	T_p	T_a	T_p	T_a	T_p	T_a	T_p	T_a	T_p	T_a	T_p	T_a
T6 (-85 °C)	-	60 °C	-	60 °C	-	60 °C	-	-40 °C	-	-40 °C	-	-

 T_p = dependent on the sensor



71258658

www.addresses.endress.com
