TI00106D/06/EN/13.15

71231038

Technical Information **Cubemass**

Coriolis flowmeter



The ultra-compact sensor for smallest quantities with easy system integration

Application

- Measuring principle operates independently of physical fluid properties such as viscosity or density
- Measuring accurately smallest quantities of liquids and gases; ideal for skid integration

Device properties

- Nominal diameter: DN 1 to 6 ($\frac{1}{24}$ to $\frac{1}{4}$ ")
- Process pressure up to 400 bar (5800 psi)
- Medium temperature up to +200 °C (+392 °F)
- Robust transmitter housing
- Modbus RS485
- Pulse output

Your benefits

- Reduced installation cost compact single-tube design
- Fewer process measuring points multivariable measurement (flow, density, temperature)
- Space-saving installation no in/outlet run needs
- Cost savings very low power consumption
- Fast commissioning pre-configured devices
- Automatic recovery of data for servicing



People for Process Automation

Table of contents

Function and system design3	
Measuring principle 3	
Measuring system 4	
Input	
Measured variable 4	
Measuring range 4	
Operable flow range 4	
Output	
Output signal 4	
Signal on alarm	
Load	
Galvanic isolation 5	
Power supply	
Terminal assignment	
Supply voltage	
Power consumption	
Power supply failure 6 Electrical connection 6	
Potential equalization	
Cable entries	
Cable specifications	
Performance characteristics7	
Reference operating conditions 7	
Maximum measured error	
Repeatability	
Response time	
Influence of medium temperature	
Influence of medium pressure 8	
Design fundamentals	
Installation9	
Installation instructions	í.
Inlet and outlet runs	
Special installation instructions 10	J
Environment 11	
Ambient temperature range 11	
Storage temperature 11	
Degree of protection 11	
Shock resistance 11	
Vibration resistance	
CIP cleaning	
SIP cleaning	
Process	
Medium temperature range	
Secondary containment pressure rating	
Pressure-temperature ratings	
Rupture disk	
Limiting flow	
Pressure loss	

System pressure	14
Mechanical construction Design/dimensions Weight Material Process connections	15 20 20
Operability Local display Remote operation	21
Certificates and approvals CE mark C-Tick symbol Ex approval Modbus certification Functional safety Pressure measuring device approval Other standards and guidelines	21 21 21 21 21 21 22
Ordering Information	22
Accessories Device-specific accessories Service-specific accessories System components	23 23
Documentation	24
Registered trademarks	24

Function and system design

Measuring principle	The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present when both translational and rotational movements are superimposed.
	$F_{C} = 2 \cdot \Delta m (v \cdot \omega)$ $F_{C} = \text{Coriolis force}$ $\Delta m = \text{moving mass}$ $\omega = \text{rotational velocity}$ v = radial velocity in rotating or oscillating system
	The amplitude of the Coriolis force depends on the moving mass Δm , its velocity v in the system, and thus on the mass flow. Instead of a constant angular velocity ω , oscillation occurs.
	 This causes the measuring tube loop through which the fluid is flowing to oscillate. The Coriolis forces produced at the measuring tube loop cause a phase shift in the oscillations of the tube loop (see illustration): If there is zero flow, i.e. when the fluid stands still, the oscillation measured at points A and B has the same phase, and thus there is no phase difference (1). Mass flow causes deceleration of the oscillation at the inlet of the tube loop (2) and acceleration at the outlet (3).

The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube loop oscillations at the inlet and outlet.

Compared to two-tube systems, other design solutions are required in single-tube systems to ensure system balance. In the case of the Cubemass, an internal reference mass is provided for this purpose. The measuring principle operates independently of temperature, pressure, viscosity, conductivity and flow profile.

Density measurement

The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising the measuring tube loop and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. Resonance frequency is thus a function of fluid density. The microprocessor utilizes this relationship to obtain a density signal.

Temperature measurement


The temperature of the measuring tube loop is determined in order to calculate the compensation factor due to temperature effects.

This signal corresponds to the process temperature and is also available as an output.

Measuring system


The measuring system consists of a transmitter and a sensor, which form a mechanical unit.

Transmitter



Configuration via MODBUS RS485, FieldCare
Mass flow, volume flow, density and temperature measurement as well as calculated variables (e.g. fluid concentrations)

Sensor



Input

Measured variable	 Mass flow (proportional to the phase difference between two sensors mounted on the me tube to register a phase shift in the oscillation) Volume flow (calculated using mass flow and density) Fluid density (proportional to the resonance frequency of the measuring tube) Fluid temperature (measured with temperature sensors) 				
Measuring range	Measuring ra	inges for liquid	S		
	DN		Range for full scale values (liquids) $\dot{m}_{min(F)}$ to $\dot{m}_{max(F)}$		
	[mm]	[in]	[kg/h]	[lb/min]	
	1	1/24"	0 to 20.00	0 to 0.735	
	2	¹ / ₁₂ "	0 to 100.0	0 to 3.675	
	4	¹ /8"	0 to 450.0	0 to 16.54	
	6	1/4"	0 to 1000	0 to 36.75	

Output

Output signal

- Pulse/frequency output
- passive
- galvanically isolated
- Open Collector
- max. 30 V DC
- max. 25 mA
- Frequency output: end frequency 100 to 5000 Hz, on/off ratio 1:1, pulse width max. 2 s
- Pulse output: pulse value and pulse polarity selectable, pulse width configurable (0.1 to 1000 ms)

	Status output passive Open Collector max. 30 V DC max. 25 mA
	 MODBUS RS485 MODBUS device type: slave Address range: 1 to 247 Functions codes supported: 03, 04, 06, 08, 16, 23 Broadcast: supported with the function codes 06, 16, 23 Physical interface: RS485 in accordance with standard EIA/TIA-485 Baudrate supported: 1200, 2400, 4800, 9600, 19200, 38400, 57600, 115200 Baud Transmission mode: RTU or ASCII Response time: typically 5 ms
Signal on alarm	Pulse/frequency output De-energized in the event of fault or power supply failure Status output De-energized in the event of fault or power supply failure MODBUS RS485 De-energized in the event of fault or power supply failure
Load	→ "Output signal"
Galvanic isolation	All circuits for outputs and power supply are galvanically isolated from each other.

Power supply

Terminal assignment	Order characteristic for	Terminal No. (outputs)			
	"inputs/outputs" 22 (+) / 23 (-)	24 (+) / 25 (-)	26 (+) / 27 (-)		
	Fixed communication board	l (permanent assignment)			
	В	Pulse / frequency /status output 2	Pulse / frequency /status output 1	MODBUS RS485	

Supply voltage

24 V DC nominal voltage (20 to 30 V DC) / 24 V AC nominal voltage (20 to 28 V AC)

Power consumption

AC: < 4.0 VA DC: < 3.2 W

Typical switch-on current at 24 V DC nominal voltage at R_i = 0.1 W of the source.

t [ms]	I [A]
0	10.0
0.1	8.0
0.2	7.5
0.5	7.0
1.0	6.0
2.0	4.0
5.0	1.5
10.0	0.125 (operating current)



Note!

The internal resistance of the source may not exceed $R_{\rm i}$ = 10 W.

Power supply failure

Lasting min. 20 ms:

• HistoROM/S-DAT: exchangeable data storage chip which stores the data of the sensor (nominal diameter, serial number, calibration factor, zero point etc.)

Electrical connection

Electrical connection			
	A A A A A A A A A A A A A A A A A A A		
	Connecting the transmitter, cable cross-section: max. 2.5 mm ² (14 AWG) A View A a Safety claw b Connection compartment cover c Signal cable: terminal Nos. 22 to 27 (shield for MODBUS RS485 is mandatory; shield for pulse, frequency and status outputs is not required, but recommended) d Cable for power supply: 20 to 28 V AC, 10 to 30 V DC – Terminal No. 1: L1 for AC, L+ for DC – Terminal No. 2: N for AC, L- for DC		
Potential equalization	No measures necessary. For explosion-protected equipment →separate Ex-documentation supplied		
Cable entries	Power supply and signal cables (outputs): • Cable entry M20 × 1.5 (8 to 12 mm / 0.31 to 0.47") • Threads for cable entries, ½" NPT, G ½"		
Cable specifications	Each compatible cable, with a temperature specification at least 20°C (68 °F) higher than the ambient temperature prevailing in the application. We recommend using a cable with a temperature specification of +80°C (176 °F).		
	MODBUS RS485 (cable type A):		
	 Characteristic impedance: 135 to 165 Ω at a measuring frequency of 3 to 20 MHz Cable capacity: < 30 pF/m (< 9.2 pF/ft) Core cross-section: > 0.34 mm² (AWG 22) Cable type: twisted pairs Loop-resistance: <110 Ω/km (<0.034 Ω/ft) 		

- Signal damping: max. 9 dB along the entire length of the cable cross-section
 Shield: Copper braided shielding or braided shielding and foil shielding

Performance characteristics

Reference operating conditions	 Error limits following ISO 11631 Water, typically +15 to +45 °C (+59 to +113 °F); 2 to 6 bar (29 to 87 psi) Specification as per calibration protocol ±5 °C (±9 °F) and ±2 bar (±30 psi) Data on the measured error based on accredited calibration rigs traced back to ISO 17025 To obtain measured errors, use the Applicator sizing tool <i>Applicator</i>: → 🖺 23.
Maximum measured error	Design fundamentals → 🗎 9 o.r. = of reading; 1 g/cm ³ = 1 kg/l; T = fluid temperature Base accuracy
	 Mass flow and volume flow (liquids) ±0.10% o.r. (mass flow) ±0.10% o.r. (volume flow)
	Mass flow (gases) ■ ±0.5% o.r.
	 Density (liquids) Reference conditions: ±0.0005 g/cm³ Standard density calibrations: ±0.02 g/cm³ (valid over the entire measuring range of the sensor →
	Temperature $\pm 0.5 \degree C \pm 0.005 \cdot T \degree C (\pm 1.0 \degree F \pm 0.003 \cdot (T - 32) \degree F)$
	Zero point stability

DN		Zero point stability		
[mm]	[in]	[kg/h]	[lb/min]	
1	¹ /24"	0.0008	0.00003	
2	1/ ₁₂ "	0.002	0.00007	
4	1/8"	0.014	0.0005	
6	1/4"	0.02	0.0007	

Flow values

Flow values as turndown parameter depending on nominal diameter.

SI units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[mm]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]
1	20.00	2.000	1.000	0.400	0.200	0.040
2	100.0	10.00	5.000	2.000	1.000	0.200
4	450.0	45.00	22.50	9.000	4.500	0.900
6	1000	100.0	50.00	20.00	10.00	2.000

US	units
00	unuu

2

4

6

¹/₁₂"

¹/8"

1/4"

	US units								
	DN	1:1	1:10	1:20	1:50	1:100	1:500		
	[in]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]		
	¹ / ₂₄ "	0.735	0.074	0.037	0.015	0.007	0.001		
	¹ / ₁₂ "	3.675	0.368	0.184	0.074	0.037	0.007		
	¹ /8"	16.54	1.654	0.827	0.330	0.165	0.033		
	1/4"	36.75	3.675	1.838	0.735	0.368	0.074		
	Accuracy of outputs o.r. = of reading; o.f.s. = of full scale value The output accuracy must be factored into the measured error if analog outputs are used, but can be ignored for fieldbus outputs (e.g. Modbus RS485). <i>Current output</i>								
	Pulse/frequen		·						
Repeatability	Accuracy: Max. $\pm 50 \%$ ppm o.r. Design fundamentals $\Rightarrow \textcircled{P} 9$ o.r. = of reading; 1 g/cm ³ = 1 kg/l; T = fluid temperature Base repeatability Mass flow and volume flow (liquids) • $\pm 0.05\%$ o.r. (mass flow) • $\pm 0.05\%$ o.r. (volume flow) Mass flow (gases) • $\pm 0.25\%$ o.r. (mass flow) Density (liquids) • ± 0.00025 g/cm ³ Temperature $\pm 0.25\%$ c $\pm 0.0025 \cdot T\%$ ($\pm 0.45\%$ $\pm 0.0015 \cdot (T - 32)\%$)								
Response time	 Response til 		it of erratic cha	uration (dampin nges in the mea		e (only mass fl	ow): after		
Influence of medium temperature		the typical mea		nperature for ze ±0.0002% of the					
Influence of medium pressure	The tables below shows the effect on accuracy of mass flow due to a difference between calibration pressure and process pressure.								
	D	N		Me	edium pressure	2			
	[mm]	[in]	[%	o.r./bar]		[% o.r./ps	si]		
	1	¹ / ₂₄ "	-	-0.001		-0.0000	7		

0

-0.005

-0.003

0

-0.0004

-0.0002

Design fundamentals

o.r. = of reading BaseAccu = base accuracy in % o.r. BaseRepeat = base repeatability in % o.r. MeasValue = measured value (in flow units consistent with the zero point stability value $\rightarrow \square$ 7) ZeroPoint = zero point stability


Calculation of the maximum measured error depending on flowrate

Flowrate (in flow units consistent with the zero point stability value $\rightarrow \square 7$)	Maximum measured error in % o.r.
$\geq \frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$	± BaseAccu
< ZeroPoint BaseAccu · 100	$\pm \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$

Calculation of the repeatability depending on flowrate

Flowrate (in flow units consistent with the zero point stability value $\rightarrow \square 7$)	Repeatability in % o.r.
$\geq \frac{\frac{1}{2} \cdot \text{ZeroPoint}}{\text{BaseRepeat}} \cdot 100$	± BaseRepeat
< $\frac{\frac{1}{2} \cdot ZeroPoint}{BaseRepeat}$ · 100	$\pm \frac{1}{2} \cdot \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$

Example for maximum measured error



E = *Error*: *Maximum measured error as* % o.r.


Q = Flow rate as %

Installation

Installation instructions	 Note the following points: The measuring device is designed for mounting on tabletops, walls or pipes. The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by pipe vibrations. No special precautions need to be taken for fittings which create turbulence (valves, elbows, T-pieces etc.) as long as no cavitation occurs.
Inlet and outlet runs	There are no installation requirements regarding inlet and outlet runs. If possible, mount the sensor upstream of fittings such as valves, T-pieces, elbows etc.

Special installation instructions

Rotating the transmitter housing




Rotating the transmitter housing

1 = Allen screw

Rupture disk

Make sure that the function and operation of the rupture disk is not impeded through the installation of the device. The position of the rupture disk is indicated on a sticker beside it. For additional information that is relevant to the process ($\rightarrow \square$ 10).

The existing connecting nozzles are not intended for the purpose of rinsing or pressure monitoring, but instead serve as the mounting location for the rupture disk.



1 Rupture disk label

2 Rupture disk with ¹/₂" NPT internal thread with 1" width across flat

3 Transport protection

Dimensions in SI units

DN	A	В	С	D	
1 to 6	33	Approx. 42	½" NPT	AF 1"	

All dimensions in [mm]

Dimensions in US units

DN	А	В	С	D	
¹ ⁄ ₂₄ to ¹ ⁄ ₄ "	1.3	Approx. 1.65	1⁄2" NPT	AF 1"	


All dimensions in [in]

Zero point adjustment

All measuring devices are calibrated accordance with state-of-the-art technology. Calibration takes place under reference conditions ($\rightarrow \square$ 7). Therefore, a zero point adjustment in the field is generally **not** required.

If a zero point adjustment is desired, please note the following points before performing one:

- Adjustment can only be performed under stable pressure conditions.
- The zero point adjustment takes place at zero flow. This can be achieved, for example, with shutoff valves upstream and/or downstream of the sensor or by using existing valves and gates.
 - Normal operation \rightarrow values 1 and 2 open
 - Zero point adjustment with process pressure \rightarrow Valve 1 open / valve 2 closed
 - Zero point adjustment without process pressure \rightarrow Valve 1 closed / valve 2 open
- A zero point adjustment is **not** possible if an error message is present.



Zero point adjustment and shutoff valves

Environment

Ambient temperature range	Sensor and transmitter: ■ Standard: -20 to +60 °C (-4 to +140 °F)
	Note! • Install the device in a shady location. Avoid direct sunlight, particularly in warm climatic regions.
Storage temperature	-40 to +80 °C (-40 to +175 °F), preferably at +20 °C (+68 °F)
Degree of protection	Standard: IP 67 (NEMA 4X) for transmitter and sensor
Shock resistance	According to IEC/EN 60068-2-31
Vibration resistance	Acceleration up to 1 g, 10 to 150 Hz, following IEC/EN 60068-2-6
CIP cleaning	Yes

SIP cleaning	Yes	Yes							
Electromagnetic compatibility (EMC)	As per IEC/EN 6	As per IEC/EN 61326 and NAMUR Recommendation NE 21							
	Process								
Medium temperature range	Sensor								
			°C (–58 to +392 ° 5 °C (–58 to +257						
	Seals								
	 Only for mounting kits with threaded connections: Viton: -15 to 200 °C (-5 to +392 °F) EPDM: -40 to +160 °C (-40 to +320 °F) Silicone: -60 to +200 °C (-76 to +392 °F) Kalrez: -20 to +275 °C (-4 to +527 °F) 								
Secondary containment	The sensor housing is filled with dry nitrogen and protects the electronics and mechanics inside.								
pressure rating		The following secondary containment pressure rating is only valid for a fully welded sensor housing and/or a device equipped with closed purge connections (never opened, as delivered).							
	D	N	Secondary cont (designed with a	ainment rating safety factor ≥ 4)	Burst pressure contai	5			
	[mm]	[in]	[bar]	[psi]	[bar]	[psi]			



Note!

¹/₂₄"

¹/₁₂"

¹/8"

1/4"

In case a danger of measuring tube failure exists due to process characteristics, e.g. with corrosive process fluids, we recommend the use of sensors whose secondary containment is equipped with special pressure monitoring connections (ordering option). With the help of these connections, fluid collected in the secondary containment in the event of tube failure can be bled off. This is especially important in high pressure gas applications. These connections can also be used for gas circulation and/or gas detection (dimensions $\rightarrow \cong 20$).

Do not open the purge connections unless the containment can be filled immediately with a dry inert gas. Use only low gauge pressure to purge. Maximum pressure: 5 bar (72.5 psi).


If a device fitted with purge connections is connected to the purge system, the maximum nominal pressure is determined by the purge system itself or by the device, depending on which component has the lower nominal pressure. If, on the other hand, the device is fitted with a rupture disk, the rupture disk is decisive for the maximum nominal pressure ($\rightarrow \cong 14$).

Pressure-temperature ratings

The following pressure-temperature ratings relate to the entire measuring device and not just to the process connection.


4-VCO-4 coupling (welded, DN 1 to 4) 8-VCO-4 coupling (welded, DN 6)

Connection material: 1.4539 (904L)




VCO coupling with mounting kit: Flange according to EN 1092-1 (DIN 2501)

Wetted parts (flange, measuring tube): 1.4539 (904L) Loose flanges (not wetted): 1.4404 (316/316L)




VCO coupling with mounting kit: Flange according to ASME B16.5

Wetted parts (flange, measuring tube): 1.4539 (904L) Loose flanges (not wetted): 1.4404 (316/316L)




VCO coupling with mounting kit: JIS B2220, flange

Wetted parts (flange, measuring tube): 1.4539 (904L) Loose flanges (not wetted): 1.4404 (316/316L)



Connection material: 1.4539 (904L)




Rupture disk	To increase the level of safety, a device version with a rupture disk with a triggering pressure of 10 to 15 bar (145 to 217.5 psi) can be used. Special mounting instructions: ($\rightarrow \square$ 10).
Limiting flow	$\rightarrow \cong$ 4, "Measuring range"
Pressure loss	To calculate the pressure loss, use the <i>Applicator</i> sizing tool ($\rightarrow \square$ 23).
System pressure	It is important to ensure that cavitation does not occur as it could influence the oscillation of the measuring tube. No special measures need to be taken for fluids which have properties similar to water under normal conditions. In the case of liquids with a low boiling point (hydrocarbons, solvents, liquefied gases) or in suction lines, it is important to ensure that pressure does not drop below the vapour pressure and that the liquid does not start to boil. It is also important to ensure that the gases that occur naturally in many liquids do not outgas. Such effects can be prevented when system pressure is sufficiently high. Consequently, it is generally best to install the sensor: • On the pump pressure side (no risk of vacuum) • At the lowest point in a riser

Mechanical construction

Design/dimensions

Field housing compact version (non-hazardous area II2G / zone 1)



Dimensions in SI units

DN	Α	В	С	D	Е	F	G	Н	J	К	L	М	N	di
1														1.3
2	160	92	10	40	90	120	292/	271/	22	168	30	120	175	2
4	100	92	10	40	90	120	226 ¹	205 ¹	22	100	50	120	175	3.9
6														5.35

¹ Short neck version DN 1 to 4: 4-VCO-4 DN 6: 8-VCO-4

All dimensions in $\left[mm \right]$

Dimensions in US units


DN	А	В	С	D	Е	F	G	Н	J	К	L	М	N	di
1/24"														0.05
1/12"	6.30	3.62	0.39	1 5 7	2 5 4	4.72	11.5/ 8.90 ¹	10.7/	0.87	6.61	1.18	4.72	6.89	0.08
1⁄8"	0.50	5.02	0.59	1.57	5.54	4.72	8.90 ¹	8.07 ¹	0.67	6.61	1.10	4.72	0.09	0.15
1/4"														0.21

¹ Short neck version DN ¹⁄₂₄ to ¹⁄₈": 4-VCO-4 DN ¹⁄₄": 8-VCO-4

All dimensions in [in]

Process connections in SI units

4-VCO-4 coupling (welded, DN 1 to 4) 8-VCO-4 coupling (welded, DN 6)




Engineering unit mm (in)

4-VCO-4 coupling (welded, DN 1 to 4): 1.4539 (904L) Order code for "process connection", option A 8-VCO-4 coupling (welded, DN 6): 1.4539 (904L) Order code for "process connection", option B									
DN	L	Р	Q						
1 to 4	175	AF 11/16"	12.5						
6	175	AF 1"	20						

All dimensions in [mm]

 $4\math{-}VCO\math{-}4$ coupling with mounting kit: NPTF threaded adapter, $\math{-}4\math{''}$ (DN 1 to 4) $8\math{-}VCO\math{-}4$ coupling with mounting kit: NPTF threaded adapter, $\math{-}2\math{''}$ (DN 6)




Engineering unit mm (in)

4-VCO-4 coupling with mounting kit: NPTF threaded adapter, ¼": 1.4539 (904L)							
DN	L	Р	Q				
1 to 4	246	AF 3⁄4"	1⁄4" NPTF				
6	246	AF 1 1/16"	½" NPTF				

All dimensions in [mm]

4-VCO-4 / 8-VCO-4 coupling with mounting kit: Flange according to EN1092-1 (DIN 2501) 4-VCO-4 / 8-VCO-4 coupling with mounting kit: ½" flange according to ASME B16.5 4-VCO-4 / 8-VCO-4 coupling with mounting kit: JIS B2220, DN 15 flange



Engineering unit mm (in)

	4-VCO-4 / 8-VCO-4 coupling with mounting kit: Flange according to EN1092-1 (DIN 2501), PN 40: 1.4539 (904L)							
DN	PN	L	Р	Q	R	S	LK	
1 to 6	40	278	95	17.3	4ר14	28	65	

All dimensions in [mm]

4-VCO-4 / 8-	4-VCO-4 / 8-VCO-4 coupling with mounting kit: ½" flange according to ASME B16.5: 1.4539 (904L)								
DN	ASME	L	Р	Q	R	S	LK		
1 to 6	Cl 150	278	88.9	15.7	4 × Ø 15.7	17.7	60.5		
1 to 6	Cl 300	278	95.2	15.7	4 × Ø 15.7	20.7	66.5		


Loose flanges (not wetted) made from stainless steel 1.4404 (316/316L) All dimensions in [mm]

4-VCO-4 / 8-VCO-4 coupling with mounting kit: JIS B2220, DN 15 flange: 1.4539 (904L)								
DN	JIS	L	Р	Q	R	S	LK	
1 to 6	10K	278	95	15	4 × Ø 15	28	70	

All dimensions in [mm]

Process connections in US units

4-VCO-4 coupling (welded, DN $^{1}\!\!\!\!/_{24}$ to $^{1}\!\!\!/_{8}")$ 8-VCO-4 coupling (welded, DN $^{1}\!\!\!/_{4}")$




Engineering unit mm (in)

4-VCO-4 coupling (welded, DN ¹ / ₂₄ to ¹ / ₈ "): 1.4539 (904L) Order code for "process connection", option A 8-VCO-4 coupling (welded, DN ¹ / ₄ "): 1.4539 (904L) Order code for "process connection", option B						
DN	L	Р	Q			
¹ / ₂₄ to ¹ / ₈ "	6.89	AF 11/16"	0.49			
1/4"	6.89	AF 1"	0.79			

All dimensions in [in]

4-VCO-4 coupling with mounting kit: NPTF threaded adapter, $\frac{1}{4}$ " (DN $\frac{1}{24}$ to $\frac{1}{8}$ ") 8-VCO-4 coupling with mounting kit: NPTF threaded adapter, $\frac{1}{4}$ " (DN $\frac{1}{4}$ ")




Engineering unit mm (in)

8-VCO-4 coupling with mounting kit: NPTF threaded adapter, ½": 1.4539 (904L)							
DN	L	Р	Q				
¹ ⁄ ₂₄ to ¹ ⁄ ₈ "	9.69	AF 34"	1⁄4" NPTF				
1/4"	9.69	AF 1 1/16"	½" NPTF				

All dimensions in [in]

4-VCO-4 / 8-VCO-4 coupling with mounting kit: Flange according to EN1092-1 (DIN 2501) 4-VCO-4 / 8-VCO-4 coupling with mounting kit: ½" flange according to ASME B16.5 4-VCO-4 / 8-VCO-4 coupling with mounting kit: JIS B2220, DN 15 flange



Engineering unit mm (in)

	4-VCO-4 / 8-VCO-4 coupling with mounting kit: Flange according to EN1092-1 (DIN 2501), PN 40: 1.4539 (904L)							
DN	PN	L	Р	Q	R	S	LK	
¹ ⁄ ₂₄ to ¹ ⁄ ₄ "	40	11	3.74	0.68	4 × Ø 0.55	1.10	2.56	

All dimensions in [in]


4-VCO-4 / 8-	4-VCO-4 / 8-VCO-4 coupling with mounting kit: ½" flange according to ASME B16.5: 1.4539 (904L)								
DN	ASME	L	Р	Q	R	S	LK		
¹ ⁄ ₂₄ to ¹ ⁄ ₄ "	Cl 150	11	3.50	0.62	4 × Ø 0.62	0.70	2.38		
¹ ⁄ ₂₄ to ¹ ⁄ ₄ "	Cl 300	11	3.75	0.62	4 × Ø 0.62	0.82	2.62		

Loose flanges (not wetted) made from stainless steel 1.4404 (316/316L) All dimensions in $\left[in \right]$

4-VCO-4 / 8-VCO-4 coupling with mounting kit: JIS B220, DN 15 flange: 1.4539 (904L)								
DN	JIS	L	Р	Q	R	S	LK	
¹ ⁄ ₂₄ to ¹ ⁄ ₄ "	10K	11	3.74	0.59	4 × Ø 0.59	1.10	2.76	

All dimensions in [in]

Purge connections / secondary containment monitoring



Dimensions in SI units

DN	А	В	С	D
1 to 6	1⁄2" NPT	30	37	33

All dimensions in [mm]

Dimensions in US units

DN	А	В	С	D
¹ ⁄ ₂₄ to ¹ ⁄ ₄ "	½" NPT	1.18	1.46	1.30

All dimensions in [in]

Weight

Compact version					
[kg]	[lb]				
5.0	11.0				

Material

Transmitter housing

Aluminium housing: powder-coated die-cast aluminium

Sensor housing / secondary containment

• Acid-resistant and alkali-resistant external surface, stainless steel 1.4301 (304)

Process connections

Process connection	Material
4-VCO-4 coupling 4-VCO-8 coupling	Stainless steel, 1.4539 (904L);
Mounting kit: flange according to EN1092-1 (DIN 2501) Mounting kit: flange according to ASME B16.5 Mounting kit: JIS B2220, flange	Stainless steel, 1.4539 (904L); Loose flange (not wetted): stainless steel, 1.4404 (F316/316L)
Mounting kit: NPTF threaded adapter ¼" Mounting kit: NPTF threaded adapter ½"	Stainless steel, 1.4539 (904L);

Measuring tube

■ 1.4539 (904L)

	Seals for mounting set
	 Viton EPDM Silicone Kalrez
Process connections	 Welded process connections 4-VCO-4 -coupling (DN 1 to 4) 8-VCO-4 coupling (DN 6)
	 Threaded process connections Flange according to EN1092-1 (DIN 2501) Flange according to ASME B16.5 JIS B2220, flange NPTF threaded adapter, ¼", (DN 1 to 4) NPTF threaded adapter, ½", (DN 6)

Operability

Local display	Display elements Status LED
Remote operation	Operation takes place using the "FieldCare" configuration and service program from Endress+Hauser and the MODBUS RS485, which can be used to configure parameters for functions and read measuring values.

Certificates and approvals

CE mark	The measuring system is in conformity with the statutory requirements of the EC Directives. Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
C-Tick symbol	The measuring system meets the EMC requirements of the Australian Communications and Media Authority (ACMA).
Ex approval	Information about currently available Ex versions (ATEX, NEC/CEC etc.) can be supplied by your Endress+Hauser sales office on request. All information relevant to explosion protection is available in separate Ex documents that you can order as necessary.
Modbus certification	The measuring device meets all the requirements of the Modbus/TCP conformity and integration test and has the "Modbus/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out and is certified by the "Modbus/TCP Conformance Test Laboratory" of the University of Michigan.
Functional safety	SIL 2: in accordance with IEC 61508/IEC 61511-1 (FDIS)

Pressure measuring device approval	 The measuring devices can be ordered with or without PED (Pressure Equipment Directive). If a device with PED is required, this must be ordered explicitly. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary. With the identification PED/G1/III on the sensor nameplate, Endress+Hauser confirms conformity with the "Basic safety requirements" of Appendix I of the Pressure Equipment Directive 97/23/EC. Devices with this identification (with PED) are suitable for the following types of fluid: Fluids of Group 1 and 2 with a steam pressure greater than, or smaller and equal to 0.5 bar (7.3 psi) Unstable gases Devices without this identification (without PED) are designed and manufactured according to good engineering practice. They correspond to the requirements of Art. 3, Section 3 of the Pressure Equipment Directive 97/23/EC. Their application is illustrated in Diagrams 6 to 9 in Appendix II of the Pressure Equipment Directive 97/23/EC.
Other standards and guidelines	 EN 60529: Degrees of protection provided by enclosures (IP code) EN 61010-1: Safety requirements for electrical equipment for measurement, control and laboratory use IEC/EN 61326: Electromagnetic compatibility (EMC requirements) NAMUR Recommendation NE 21: Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment NAMUR Recommendation NE 43: Standardization of the signal level for the breakdown information of digital transmitters with analog output signal NAMUR Recommendation NE 53: Software of field devices and signal-processing devices with digital electronics

Ordering Information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select country
 → Instruments → Select device → Product page function: Configure this product
- From your Endress+Hauser Sales Center: www.endress.com/worldwide



Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the Transmitter

Accessories	Description
Electronics module	Complete plug-in electronics module.

For the Sensor

Accessories	Description
Mounting set for sensor	Mounting set, comprising: – 2 process connections – Seals
Mounting plate for sensor	Mounting plate, comprising: – mounting plate – 4 × M5

Service-specific accessories

Accessories	Description
Applicator	 Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections Graphic illustration of the calculation results Administration, documentation and access to all project-related data and
	parameters over the entire life cycle of a project.
	 Applicator is available: Via the Internet: https://wapps.endress.com/applicator On CD-ROM for local PC installation
W@M	Life cycle management for your plant. W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress+Hauser also takes care of maintaining and updating the data records.
	W@M is available:Via the Internet: www.endress.com/lifecyclemanagementOn CD-ROM for local PC installation
Fieldcheck	Tester/simulator for testing flowmeters in the field. When used in conjunction with the "FieldCare" software package, test results can be imported into a database, printed and used for official certification. Contact your Endress+Hauser representative for more information.
FieldCare	FieldCare is Endress+Hauser's FDT-based plant asset management tool and allows the configuration and diagnosis of intelligent field devices. By using status information, you also have a simple but effective tool for monitoring devices. The Proline flowmeters are accessed via a service interface or via the service interface FXA193.
FXA291	Service interface from the measuring device to the PC for operation via FieldCare.

System components

Accessories	Description
Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all the relevant process variables. Measured values are recorded correctly, limit values are monitored and measuring points analysed. The data are stored in the 256 MB internal memory and also on a DSD card or USB stick. Memograph M boasts a modular design, intuitive operation and a comprehensive security concept. The ReadWin [®] 2000 PC software is part of the standard package and is used for configuring, visualizing and archiving the data captured. The mathematics channels which are optionally available enable continuous monitoring of specific power consumption, boiler efficiency and other parameters which are important for efficient energy management.

Documentation

- Flow measurement (FA00005D/06)
- System Information Promass (SI00032D/06)
- Operating Instructions MODBUS RS485 (BA00142D/06)
- Description of Device Parameters MODBUS RS485 (GP00005D/06)
- Ex-Supplementary documentation ATEX (II2G): (XA00146D/06)
- Ex-Supplementary documentation NEC/CEC (Div. 1): (XA00147D/06)
- Ex-Supplementary documentation NEPSI (Zone 1, Zone 21): (XA00148D/06)

Registered trademarks

 $\mathsf{KALREZ}^{\texttt{B}}$ and $\mathsf{VITON}^{\texttt{B}}$

Registered trademarks of E.I. Du Pont de Nemours & Co., Wilmington, USA $\operatorname{Modbus}^{\scriptscriptstyle \otimes}$

Registered trademark of the SCHNEIDER AUTOMATION, INC.

Applicator[®], FieldCare[®], Fieldcheck[®], HistoROM[™], S-DAT[®] Registered or registration-pending trademarks of the Endress+Hauser Group

www.addresses.endress.com

