# **Technical Information**

# Liquicap M FTI51, FTI52

# Capacitance Point level switch for liquids



#### Application

The Liquicap M FTI5x is used for point level detection. It is preferably used for the following measuring tasks:

- Detection of liquids and pastes that are highly viscous and tend to form buildup
- Interface detection of different liquids (e.g. oil on water)
- Two-point control (e.g. pump control) with just one process connection
- Foam detection of conductive liquids

Thanks to its robust and tried-and-tested construction, the probe can be used both in vacuums and in overpressure up to 100 bar. The materials used allow operating temperatures from  $-80\,^{\circ}\text{C}$  to  $+200\,^{\circ}\text{C}$ .

#### Your benefits

- Active buildup compensation for high-viscosity media
- Easy and fast commissioning at the press of a button
- Universal application thanks to wide range of certificates and approvals
- Corrosion-resistant, FDA-listed materials in contact with the process
- Two-stage overvoltage protection against discharge from the container
- Short reaction times
- No need for recalibration after replacing electronics
- Use in safety systems with specific requirements in terms of functional safety to SIL2/SIL3
- Automatic monitoring of electronics

# Table of contents

Function and system design	.4
Measuring principle	
Interface detection	
Foam detection	
Measuring system Electronic inserts	
System integration via Fieldgate	
System integration via Pielugate	J
Operating conditions: Installation	10
Installation instructions	
Support for marine approval (GL)	11
With separate housing	12
On anothing conditions, Environment	١ /.
Operating conditions: Environment	
Storage temperature	
Climate class	
Vibration resistance	
Shock resistance	14
Cleaning	
Degree of protection	
Electromagnetic compatibility (EMC)	14
Operating conditions: Process	15
Process temperature range	
Influence of process temperature	
Process pressure limits	
Pressure and temperature derating	
Liquicap M operational range	18
Mechanical construction 1	۱9
Mechanical construction         1           Overview         2           Weight         3	19
Overview	19 28 28
Overview	19 28 28
Overview Weight Technical data: probe Material	19 28 28 28
Overview          Weight          Technical data: probe          Material          Input	19 28 28 28 28
Overview          Weight          Technical data: probe          Material          Input          Measured variable	19 28 28 28 28 <b>29</b>
Overview          Weight          Technical data: probe          Material          Input	19 28 28 28 29 29
Overview	19 28 28 28 29 29
Overview	19 228 228 228 229 229 229
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output  3	19 228 228 228 229 229 229
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode	19 28 28 228 29 29 29 29 30 30
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay	19 28 28 228 29 29 29 29 30 30 30
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode	19 28 28 228 29 29 29 29 30 30 30
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation	19 28 28 28 29 29 29 29 30 30 30 30 30
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation  Electronic insert FEI51 (AC 2-wire)	19 28 28 28 29 29 29 29 30 30 330 330
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation	19 28 28 28 29 29 29 29 30 30 30 330 330
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation  Electronic insert FEI51 (AC 2-wire) Power supply Electrical connection Signal on alarm	19 28 228 228 29 29 29 29 30 30 330 330 331 331
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation  Electronic insert FEI51 (AC 2-wire) Power supply Electrical connection Signal on alarm Output signal	19 28 28 28 29 29 29 30 30 330 330 331 331 331
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation  Electronic insert FEI51 (AC 2-wire) Power supply Electrical connection Signal on alarm	19 28 28 28 29 29 29 30 30 330 330 331 331 331
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation  Electronic insert FEI51 (AC 2-wire) Power supply Electrical connection Signal on alarm Output signal Connectable load	19 28 28 28 29 29 29 30 30 330 330 331 331 331
Overview Weight Technical data: probe Material  Input Measured variable Measuring range Measuring conditions  Output Switch behavior Fail-safe mode Switching delay Galvanic isolation  Electronic insert FEI51 (AC 2-wire) Power supply Electrical connection Signal on alarm Output signal	19 228 28 29 29 29 29 30 30 330 331 331 331 331

Electrical connection Output signal Signal on alarm Connectable load	. 32 . 32
Electronic insert FEI53 (3-wire)  Power supply  Electrical connection  Output signal  Signal on alarm  Connectable load	. 33 . 33 . 33 . 33
Electronic insert FEI54 (AC/DC with relay output).  Power supply	
Electrical connection Output signal Signal on alarm Connectable load	. 34 . 34 . 34
Electronic insert FEI55 (8/16 mA; SIL2/SIL3)	35
Power supply Electrical connection Output signal Signal on alarm Connectable load	. 35 . 35 . 35
Electronic insert FEI57S (PFM)	36
Power supply Electrical connection Output signal Signal on alarm Connectable load	. 36 . 36 . 36 . 36
Electronic insert FEI58 (NAMUR H-L edge)	37
Power supply Electrical connection Output signal Signal on alarm Connectable load	. 37 . 37 . 37
Power supply	38
Electrical connection  Connector  Cable entry	. 38 . 38
Performance characteristics	39
Reference operating conditions	. 39
Human interface	
Electronic inserts	. 41

Certificates and approvals	. 43
CE mark	. 43
RoHS	. 43
RCM-Tick marking	. 43
Ex approval	. 43
EAC conformity	
Other standards and guidelines	
Additional approvals	
CRN approval	
Pressure Equipment Directive 2014/68/EU (PED)	. 44
Ordering information	. 44
Accessories	. 44
Protective cover	
Shortening kit for FTI52	
Overvoltage protection HAW56x	
Weld-in adapter	
Documentation	. 45
Technical Information	. 45
Operating Instructions	

# Function and system design


#### Measuring principle

The principle of capacitance point level detection is based on the change in capacitance of the capacitor due to the probe being covered by liquid. The probe and container wall (conductive material) form an electric capacitor. When the probe is in air (1), a certain low initial capacitance is measured. When the container is filled, the capacitance of the capacitor increases the more the probe is covered (2), (3). The point level switch switches when the capacitance  $C_S$  specified during calibration is reached. In addition, a probe with inactive length ensures that the effects of medium buildup or condensate near the process connection are avoided. Active buildup compensation compensates influences resulting from buildup on the probe.



#### Note!

A ground tube is used as a counterelectrode for containers made of nonconductive materials.




- R: Conductivity of the liquid
- C: Capacitance of the liquid
- $C_A$ : Initial capacitance (probe not covered)
- $C_S$ : Switching capacitance
- ΔC: Change in capacitance

#### **Function**

The selected electronic insert of the probe determines the change in capacitance of the liquid depending on how much the probe is covered and thereby allows precise switching at the point level calibrated for this.

### Interface detection




- 1.) Water, for example (the medium must be conductive  $\geq$  100  $\mu S/cm$ )
- 2.) Emulsion
- 3.) Oil, for example (nonconductive medium  $< 1 \mu S/cm$ )

A prior adjustment also ensures a certain and definite switch point even if the emulsion layer is of varying thickness.

# Foam detection

Foam detection for conductive liquids.



1.) Liquid 2.) Foam



Note!

Preferably use partially insulated probes.


# Measuring system

The make-up of the measuring system depends on the electronic insert selected.

# Point level switch

The compact measuring system consists of:

- The Liquicap M FTI51 or FTI52 point level switch
- An electronic insert FEI51, FEI52, FEI54




# Pump control (∆s)



Note

Only possible with a fully insulated probe.




The point level switch can also be used to control a pump, for example, where the switch-on and switch-off point can be freely defined.

#### Point level switch

Liquicap M FTI5x with electronic versions FEI53, FEI57S and FEI58 for connecting to a separate switching unit.

The complete measuring system consists of:

- The capacitance Liquicap M FTI51 or FTI52 point level switch
- An electronic insert FEI53, FEI57S, FEI58
- A transmitter power supply unit (see table below)



\* Only possible with FEI53


The following table shows the transmitter power supply units available which can be operated with electronic inserts FEI53, FEI57S and FEI58.

Electronic insert	FEI57S	FEI53	FEI58
Transmitter power supply unit			
FTC625 (from SW V1.4)	Х	-	_
FTC325	X	Х	
FTL325N	_	-	Х
FTL375N	_	-	Х
FTC470Z	Х	-	_
FTC471Z	X	-	_

#### Point level switch 8/16 mA

The complete measuring system consists of:

- The Liquicap M FTI51 or FTI52 point level switch
- The FEI55 electronic insert
- A transmitter power supply unit, e.g. RN221N, RNS221, RMA421, RMA422



#### **Electronic inserts**

#### FEI51

Two-wire AC connection

- Load switched directly into the power supply circuit via the thyristor
- Point level adjustment at the touch of a button

#### FEI52

3-wire direct current version:

- Switch the load via the transistor (PNP) and separate supply voltage connection
- Point level adjustment at the touch of a button

#### FEI53

3-wire direct current version with 3 to 12 V signal output:

- For separate switching unit, Nivotester FTC325 3-WIRE
- Self-test from the switching unit without changing levels
- Point level adjustment at the touch of a button

#### FFI54

Universal current version with relay output:

- Switch the loads via 2 floating changeover contacts (DPDT)
- Point level adjustment at the touch of a button

#### FFIS

Signal transmission 8/16 mA on two-wire cabling:

- SIL2 approval for the hardware
- SIL3 approval for the software
- For separate switching unit (e.g. RN221N, RNS221, RMA421, RMA422)
- Point level adjustment at the touch of a button

#### FEI579

PFM signal transmission (current pulses are superimposed on the supply current):

- For separate switching unit with PFM signal transmission e.g. FTC325 PFM, FTC625 PFM and FTC470Z/471Z
- Self-test from the switching unit without changing levels
- Point level adjustment at the touch of a button
- Cyclical checking (function check) from the switching unit.

#### FEI58 (NAMUR)

Signal transmission H-L edge 2.2 to 3.5 / 0.6 to 1.0 mA as per IEC 60947-5-6 on two-wire cable:

- For a separate switching unit (e.g. Nivotester FTL325N and FTL375N)
- Point level adjustment at the touch of a button
- Connection cables and slaves tested at the touch of a button



#### Note!

For additional information see  $\rightarrow \stackrel{\triangle}{=} 31 \text{ ff.}$ 


# System integration via Fieldgate

#### Vendor managed inventory

The remote interrogation of tank or silo levels via Fieldgate enables suppliers of raw materials to gather information about the current inventories of their regular customers at any time and, for example, take this into account in their own production planning. The Fieldgate monitors the configured point levels and automatically triggers the next order as required. Here, the range of possibilities ranges from simple requisitioning by e-mail through to fully automatic order processing by incorporating XML data into the planning systems on both sides.

#### Remote maintenance of measuring systems

Not only does Fieldgate transmit the current measured values, it also alerts the standby personnel responsible by e-mail or SMS as required. Fieldgate forwards the information transparently. In this way, all options of the operating software in question are available remotely. By using remote diagnosis and remote configuration some onsite service operations can be avoided and all others can at least be planned and prepared better.



L00-FTI5xxxx-14-00-06-en-00

# Operating conditions: Installation

#### **Installation instructions**


Liquicap M FTI51 (rod probe) can be installed from above, from below and from the side. Liquicap M FTI52 (rope probe) can be installed vertically from above.



#### Note!


- The probe may not come into contact with the container wall!
- Recommended distance from the container floor:  $\geq$ 10 mm.
- Do not install probes in the area of the filling curtain!
- Make sure the probe is at a sufficient distance from the agitator.
- If multiple probes are mounted next to each other, a minimum distance of 500 mm (19.7 in) between the probes must be observed.
- In the event of severe lateral loads, use rod probes with a ground tube.

#### For containers that conduct electricity e.g. steel tanks



L00-FTI5xxxx-11-06-xx-xx-001

#### For containers that do not conduct electricity e.g. plastic tanks



Probes with ground tube and grounding (Dimensions mm (in))


### Support for marine approval (GL)

Fully insulated rod probes can be supported conductively or non-conductively. Partially insulated rod probes may only be supported with insulation at the uninsulated probe end.



#### Note!

Rod probes with a diameter of 10 mm and 16 mm have to be supported with a length  $\geq$  1 m (see drawing).



# Example for calculating distances: Probe length L = 2000 mm.

L/4 = 500 mm

L/2 = 1000 mm


Measured from the end of the probe rod = 300 mm.

# With separate housing



#### Note!

- The maximum connection length between the probe and the separate housing is 6 m (L4). When ordering a device with a separate housing, the desired length must be specified.
- Maximum total length: L1 + L4 = 10 m
- If the connecting cable is to be shortened or passed through a wall, it must be separated from the process connection.



Rod length L1 max. 4 m Rope length L1 max. 9.7 m (the maximum total length of L1 + L4 should not exceed 10 m).

# Extension heights: separate housing

Housing side: wall mounting

Housing side: pipe mounting

Sensor side

T≥ 100 mm

T≥ 100 mm

L00-FMI5xxxx-06-05-xx-x



#### Note!

- $\blacksquare$  The cable has a bending radius of  $r \geq 100 \ mm$
- Connecting cable: ø10.5 mm
- Outer jacket: silicone, notch-resistant


	, ,	Stainless steel housing (F15)	Aluminum housing (F17)
B (mm)	76	64	65
H1 (mm)	172	166	177

		<b>H4</b> (mm)	D (mm)
Probes Ø10 mm rod		66	38
Probes Ø16 mm rod or rope (without fully insulated inactive length)	G 1/2", G 3/4", G 1", NPT 1/2", NPT 3/4", NPT 1", Clamp 1", Clamp 1 1/2", Universal Ø44, flange < DN 50, ANSI 2", 10K50		38
	G11/2", NPT11/2", Clamp 2", DIN 11851, flanges ≥ DN 50, ANSI 2", 10K50	89	50
Probes Ø 22 mm rod or rope (with fully insulated inactive length)		89	38

#### Wall holder unit



- The wall holder unit is part of the scope of supply for device versions with a separate housing.
  The wall holder unit first has to be screwed to the separate housing before you can use it as a drilling template. The distance between the holes is reduced by screwing it to the separate housing.



Dimensions mm (in)

# **Operating conditions: Environment**

#### Ambient temperature range

- -50 to +70 °C
- -40 to +70 °C (with F16 housing)
- Observe derating  $\rightarrow 15$
- If operating outdoors, use a protective cover!  $\rightarrow \stackrel{\triangle}{=} 44$ .

#### Storage temperature

-50 to +85 °C

Climate class

DIN EN 60068-2-38/IEC 68-2-38: test Z/AD

Vibration resistance

DIN EN 60068-2-64/IEC 68-2-64: 20 Hz– 2000 Hz;  $0.01 g^2/Hz$ 

Shock resistance

DIN EN 60068-2-27/IEC 68-2-27: 30 g acceleration

#### Cleaning

#### Housina:

When cleaning, make sure that the cleaning agent used does not corrode the housing surface or the seals.

#### Probe:

Depending on the application, buildup (contamination and soiling) can form on the probe rod. A high degree of material buildup can affect the measurement result. If the medium tends to create a high degree of buildup, regular cleaning is recommended. When cleaning, it is important to make sure that the insulation of the probe rod is not damaged. If cleaning agents are used make sure the material is resistant to them!

### Degree of protection

	IP66*	IP67*	IP68*	NEMA4X**
Polyester housing F16	X	X	-	X
Stainless steel housing F15	X	X	-	X
Aluminum housing F17	X	X	-	X
Aluminum housing F13	X	_	X***	X
with gas-tight process seal				
Stainless steel housing F27	X	X	X***	X
Aluminum housing T13	X	_	X***	X
with gas-tight process seal and separate				
connection compartment (Ex d)				
Separate housing	X	_	X***	X

<sup>\*</sup> As per EN60529

# Electromagnetic compatibility (EMC)

- Interference emission to EN 61326, Electrical Equipment Class B
   Interference immunity in accordance with EN 61326, Appendix A (Industrial) and NAMUR

   Recommendation NE 21 (EMC)
- A usual commercial instrument cable can be used.

<sup>\*\*</sup> As per NEMA 250

<sup>\*\*\*</sup> Only with M20 cable entry or G1/2 thread

# **Operating conditions: Process**

#### Process temperature range


The following diagrams apply for:

- Rod and rope version
- Insulation: PTFE, PFA, FEP
- Standard applications outside hazardous areas




The temperature is restricted to  $T_a$  –40  $^{\circ}$ C if the polyester housing F16 is used or if additional option B is selected (free from paint-wetting impairment substances, only FTI51).

# With compact housing



T<sub>a</sub>: Ambient temperature  $T_P$ : Process temperature

#### With separate housing



 $T_a = Ambient temperature$ 

 $T_P = Process temperature$ 

<sup>\*</sup> The permitted ambient temperature at the separate housing is the same as indicated for the compact housing  $\rightarrow 15$ .

# Influence of process temperature

Error in case of fully insulated probes typically 0.13%/K related to the full scale value.

#### **Process pressure limits**

#### Probe ø10 mm, ø14 mm (including insulation)

-1 to 25 bar (observe dependencies: process temperature and process connection →  $\stackrel{\triangle}{=}$  15 and →  $\stackrel{\triangle}{=}$  21).

#### Probe ø16 mm (including insulation)

- -1 to 100 bar (observe dependencies: process temperature and process connection  $\rightarrow$   $\stackrel{ }{=}$  15 and  $\rightarrow$   $\stackrel{ }{=}$  21).
- In the event of an inactive length, the maximum permitted process pressure is 63 bar
- In the event of CRN approval and inactive length, the maximum permitted process pressure is 32 bar.

#### Probe ø22 mm (including insulation)

-1 to 50 bar (observe dependencies: process temperature and process connection →  $\stackrel{ }{=}$  15 and →  $\stackrel{ }{=}$  21).

Refer to the following standards for the pressure values permitted at higher temperatures:

- EN 1092-1: 2005 Table, Appendix G2
  With regard to its resistance/temperature property, the material 1.4435 is identical to 1.4404 (AISI 316L) which is grouped under 13E0 in EN 1092-1 Tab. 18. The chemical makeup of the two materials can be identical.
- ASME B 16.5a 1998 Tab. 2-2.2 F316
- ASME B 16.5a 1998 Tab. 2.3.8 N10276
- IIS B 2220

The lowest value from the derating curves of the device and the selected flange applies.

# Pressure and temperature derating


For process connections  $\frac{1}{2}$ ",  $\frac{3}{4}$ ", 1", flanges < DN50, < ANSI 2", < JIS 10K (10 and 14 mm rod) For process connections  $\frac{3}{4}$ ", 1", flanges < DN50, < ANSI 2", < JIS 10K (16 mm rod)

Rod insulation: PTFE, PFA Rope insulation: FEP, PFA



Note!

See also "Process connections"  $\rightarrow \stackrel{\triangle}{=} 21$ .



 $P_p$ : Process pressure  $T_p$ : Process temperature


# For process connections 1½", flanges $\geq$ DN50, $\geq$ ANSI 2", $\geq$ JIS 10K (16 mm rod)

Rod insulation: PTFE, PFA Rope insulation: FEP, PFA




Note!

See also "Process connections"  $\rightarrow \, \stackrel{ riangle}{ riangle} \, 21$ 



 $P_p$ : process pressure


# With a fully insulated inactive length (22 mm rod):



 $P_p$ : Process pressure  $T_p$ : Process temperature

 $T_p$ : process temperature \* For probes with an inactive length .

# Liquicap M operational range



Typical DK values (dielectric constant)					
Air	1				
Vacuum	1				
Liquefied gases, general	1.2 - 1.7				
Gasoline	1.9				
Cyclohexane	2				
Diesel fuel	2.1				
Oils, general	2 - 4				
Methyl ether	5				
Butanol	11				
Ammonia	21				
Latex	24				
Ethanol	25				
Caustic soda	22 - 26				
Acetone	20				
Glycerine	37				
Water	81				



#### Note!

Further information and dielectric constants (DC values) in the Download Area of the Endress+Hauser web site:

- the Endress+Hauser DC manual (CP01076F)
- the Endress+Hauser "DC Values App" (available for Android and iOS)


# Mechanical construction



Note!


The dimensions on the following pages are indicated in mm.

#### Overview




# Housing


Polyester housing F16



Stainless steel housing F15




Aluminum housing F17




*Aluminum housing F13* with gas-tight process seal

Stainless steel housing F27 with gas-tight process seal



Aluminum housing T13 with separate connection compartment and gas-tight process seal



# Housing heights with adapter

	Polyester housing F16	Stainless steel housing F15	Aluminum housing F17	Aluminum housing F13	Stainless steel housing F27	Aluminum housing T13
	L00-FT15xxxx-06-05-xx-xx-044	L00-FTI5xxxx-06-05-xx-xx-046	L00-FTI5xxxx-06-05-xx-xx-045	L00-FT15xxxx-06-05-xx-xx-048	L00-FTI5xxxx-04-05-xx-xx-04-08	L00-FTI5xxxx-06-05-xx-xx-047
Order code	2	1	3	4	4	5
H1	143	141	150	194	194	210

#### **Process connections**

	Thread G	Thread NPT	Threaded pipe joint	Tri-Clamp	Tri-Clamp clad
	ST AF	AF AF	2	<b>E E E E</b>	<b>E</b>
	L00-FMI5xxxx-06-05-xx-en-007	L00-FMI5xxxx-06-05-xx-en-007	L00-FMI5xxxx-06-05-xx-xx-040	L00-FMI5xxxx-06-05-xx-xx-041	L00-FMI5xxxx-06-05-xx-xx-069
	(DIN EN ISO228-I)	(ANSI B 1.20.1)	(EN 11851)	(ISO2852)	(ISO2852)
Rod probes Ø10, rope probes					
For pressures up to	25 bars	25 bars	25 bars	25 bar**	
Version / order code	G ½ / GCJ G ¾ / GDJ G 1 / GEJ	NPT ½ / RCJ NPT ¾/ RDJ NPT 1 / REJ	DN50 PN40 / MRJ	DN25 (1") / TCJ DN38 (1½") / TJJ	
Dimensions	H2 = 38 H3 = 19 AF = 41	H2 = 38 H3 = 19 AF = 41	H2 = 57	H2 = 57	
Surface roughness***			≤ 0.8 µm	≤ 0.8 µm	
Additional information	Elastomer flat seal			EHEDG*, 3A*	
Rod probes Ø14					
For pressures up to	25 bars	25 bars	25 bars	25 bar**	16 bar** 16 bar**
Version / order code	G ¾ / GDJ G 1 / GEJ	NPT ¾/ RDJ NPT 1 / REJ	DN50 PN40 / MRJ	DN25 (1") / TCJ DN38 (1½") / TJJ DN40-51 (2") / TDJ	DN38 / DN40-51 TJK TDK (1½") (2")
Dimensions	H2 = 38 H3 = 19 AF = 41	H2 = 38 H3 = 19 AF = 41	H2 = 66	H2 = 66	H2 = 66
Surface roughness***			≤ 0.8 µm	≤ 0.8 µm	≤ 0.8 µm
Additional information	Elastomer flat seal			EHEDG, 3A	EHEDG, 3A

 $<sup>^{\</sup>star}$  The EHEDG, 3A certificate only applies to probes with a fully insulated probe rod. It does not apply to probes with an inactive length or active buildup compensation.

\*\*\* In the event of CRN approval, the maximum permitted process pressure is 11 bar.

\*\*\* Does not apply for inactive lengths.

	Thread G		Thread N	PT	Threaded pipe joint	Tri-Clamp		Tri-Clam	clad
Rod probes Ø16, rope probe	es								
For pressures up to	25 bars	100 bar	25 bars	100 bar	40 bar	16 bar**	16 bar**	16 bar**	16 bar**
Version / order code	G ¾ / GDJ G 1 / GEJ	G 1½ / GGJ	NPT ¾/ RDJ NPT 1 / REJ	NPT 1½/RGJ	DN50 PN40 / MRJ	DN38 / TNJ (1½")	DN40-51 / TDJ (2")	DN38 / TJK (1½")	DN40-51 TDK (2")
Dimensions	H2 = 38 H3 = 19 AF = 41	H2 = 41 H3 = 25 AF = 55	H2 = 38 H3 = 19 AF = 41	H2 = 41 H3 = 25 AF = 55	H2 = 66	H2 = 98***	H2 = 66	H2	= 66
Surface roughness***	-	-			≤ 0.8 µm	≥ 0.8	3 µт	≤ 0.8	8 µm
Additional information	Elastomer	flat seal				EHEDG*, 3A*		EHED	OG, 3A
Rod probes Ø22, rope probe	es				l.	1	1	1	
For pressures up to	50 bar		50 bar			-	-		
Version / order code	G 1½ / GGJ		NPT 1½/ RGJ			-	-	-	
Dimensions	H2 = 85 H3 = 25 AF = 55		H2 = 85 H3 = 25 AF = 55			-	-	-	
Additional information	Elastomer f	flat seal				-	-	-	

<sup>\*</sup> The EHEDG, 3A certificate only applies to probes with a fully insulated probe rod. It does not apply to probes with an inactive length or active buildup 

	Flanges	Hygiene connection	Hygiene connection	Hygiene connection
	L00-FMI5xxxx-06-05-xx-xx-042	AF ELOO-FMI5xxxx-06-05-xx-en-009	AF EL L00-FMI5xxxx-06-05-xx-en-010	LOO-FMISxxxx-06-05-xx-xx-043
	(EN1092-1) (ANSI B 16.5) (JIS B2220)	With flush-mounted seal	With flush-mounted seal	Adapter 44 mm with flush-mounted seal
Rod probes Ø10, rope probes				
For pressures up to	Max. 25 bar (depends on flange)	25 bars	25 bars	
Version / order code	EN / B## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ ANSI / A## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ JIS /K## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+	G ¾ / GQJ	G 1 / GWJ	
Dimensions	H2 = 57	H2 = 31 H3 = 26 AF = 41	H2 = 27 H3 = 30 AF = 41	
Additional information	Also clad (PTFE) for aggressive process media	Weld-in adapter see "Accessories" EHEDG*, 3A*	Weld-in adapter see "Accessories" EHEDG, 3A	
Rod probes ∅14			,	
For pressures up to	Max. 25 bar (depends on flange)		25 bars	16 bar (tightening torque 10 Nm)

	Flanges	Hygiene connection	Hygiene connection	Hygiene connection
Version / order code	EN / B## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ ANSI / A## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ JIS /K## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+		G 1 / GWJ	Universal adapter / UPJ
Dimensions	H2 = 57		H2 = 27 H3 = 30 AF = 41	H2 = 57
Additional information	Also clad (PTFE)		Weld-in adapter see "Accessories" EHEDG, 3A	Universal adapter see "Accessories"
Rod probes Ø16, rope probe	s	<u>'</u>		
For pressures up to	Max. 100 bar (depends on flange) Max. 50 bar (with active buildup compensation)			16 bar (tightening torque 10 Nm)
Version / order code	EN /B## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ ANSI /A## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ JIS /K## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+			Universal adapter / UPJ
Dimensions	H2 = 66			H2 = 57
Additional information	Also clad (PTFE)			Universal adapter see "Accessories"
Rod probes Ø22, rope probe	s	<u>'</u>		
For pressures up to	Max. 50 bar (depends on flange)			
Version / order code	EN /B## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ ANSI /A## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+ JIS /K## $\rightarrow$ $\stackrel{\triangle}{=}$ 44+			
Dimensions	H2 = 111			
Additional information	Only clad (PTFE)			

<sup>\*</sup> The EHEDG, 3A certificate only applies to probes with a fully insulated probe rod. It does not apply to probes with an inactive length or active buildup compensation.

# 1. Fully insulated rod probes FTI51



#### Note!

- The active rod probe is always fully insulated (dimension L1).
- Total length of probe from sealing surface: L = L1 + L3 (+ 125 mm with active buildup compensation +  $H3^*$ )
- Thickness of insulation with probe rod diameter 10 mm = 1 mm; 16 mm = 2 mm; 22 mm = 2 mm
- Length tolerances L1, L3: < 1 m: 0 to -5 mm, 1 to 3 m: 0 to -10 mm, 3 to 6 m: 0 to -20 mm

	Rod pro	be	Rod pro with gr tube		Rod pro with in length	active		elength	Rod probe with fully insulated inactive length	Rod pro with ac buildup comper	tive		)
G NPT			L1		L1 L3		L1 L3		L1 L3	L1 125		L1 125 L3	
L00-FMI5xxxx-06-05-xx-xx-061													06-05-xx-xx-060
Total length (L)	100			.4000		6000		.6000	3004000		.4125		.6000
Active rod length (L1)	100			.4000		4000		.4000	1503000		.4000		.4000
Inactive rod length (L3)	-			-		2000		.2000	1501000		-		.2000
ø Probe rod	10	16	10	16	10	16	10	16	22**	10	16	10	16
ø Ground tube			22	43			22	43					
ø Inactive length					22	43	22	43	22**			22	43
ø Active buildup compensation										19	26	19	26
Length (mm) active buildup compensation	-	-	-		-	-	-	-		12	25	1.	25
Lateral loading capacity (Nm) at 20 °C	<15	<30	<40	<300	<30	<60	<40	<300	<25	<30	<60	<30	<60
For use in agitating tanks	-			Х	_	-		Х		_	-	-	
For aggressive liquids	Σ	Υ	-		-	-	-	-	Х	-	-	-	
For high-viscosity liquids	Σ	ζ	-		2	ζ	-	-	Х	2	Χ		X
For use in plastic tanks	-	-	2	X	-	-	2	X		-		-	
For use in mounting nozzles	-	-	-	-	2	ζ	2	X	Х	-	-		X
In the event of condensate on tank ceiling	-	-	-	-	2	ζ	2	X	Х	-	-	2	X
For high-viscosity conductive liquids	-	-	-		-	-	-	-		2	Χ	2	X

<sup>\*</sup> H3 = Thread height (important for calculating the exact probe length for process connections with a thread.) ightarrow ightharpoons 21

<sup>\*\*</sup> Probe tube

# 2. Fully insulated rod probes FTI51 for hygiene applications



- Total length of probe from sealing surface: L = L1 (+ 125 mm with active buildup compensation)
   Thickness of insulation with probe rod diameter 14 mm = 1 mm; 16 mm = 2 mm
   Length tolerances L1, L3: < 1 m: 0 to −5 mm, 1 to 3 m: 0 to −10 mm, 3 to 6 m: 0 to −20 mm</li>

	Rod probe with clad Tri-Clamp	Rod probe with fully insulated active buildup compensation and clad Tri-Clamp
316L PTFE		L1 125
Total length (L)	1004000	2002125
Active rod length (L1)	1004000	752000
Probe rod diameter	16	14
ø Ground tube		
ø Inactive length		
ø Active buildup compensation		14
Length, active buildup compensation		125
Lateral loading capacity (Nm) at 20 °C	<30	<15
For use in agitating tanks		
For aggressive liquids	Х	X
For high-viscosity liquids	Х	X
For use in plastic tanks		
For use in mounting nozzles		X
In the event of condensate on tank ceiling		X
For high-viscosity conductive liquids		X

# ${\bf 3.\ Partially\ insulated\ rod\ probes\ FTI51}$ For a switch point with millimeter accuracy in conductive liquids



- Total length of probe from sealing surface: L = L1 + L3 (+ 125 mm with active buildup compensation
- Thickness of partial insulation with probe rod diameter 10 mm = 1 mm; 16 mm = 2 mm
- Length tolerances L1, L3: < 1 m: 0 to -5 mm, 1 to 3 m: 0 to -10 mm, 3 to 6 m: 0 to -20 mm

	Rod pro	be	Rod prob ground t		Rod pro inactive		Rod pro inactive and gro		Rod pro active b compen	uildup	Rod prob inactive and active buildup compens	length ve
G NPT  H3* G, NPT  L00-FMI5xxxx-06-05-xx-xx-06-1	L1		L1 L2		L1 L3		L1 L3 L3		L1 125		L126 L3	26-05-xx-xx-062
Total length (L)	100	4000	100	.4000	200	.6000	200	.6000	225	.4000	100	
Active rod length (L1)	100	4000	100	.4000	100	.4000	100	.4000	100	.4000	100	4000
Inactive rod length (L3)	-	-		-	100	.2000	100	.2000	-	-	100	2000
Length of partial insulation (L2)	75	3950	75	3950	75	3950	75	3950	753	3950	753	3950
Probe rod diameter	10	16	10	16	10	16	10	16	10	16	10	16
ø Inactive length / ground tube	-	-	22	43	22	43	22	43	-	-	22	43
ø Active buildup compensation	-	-	-	-	1	-	-	-	19	26	19	26
Length, active buildup compensation	-	-		-	-		-		12	25	12	25
Lateral loading capacity (Nm) at 20 °C	<15	<30	<40	<300	<30	<60	<40	<300	<30	<60	<30	<60
For use in agitating tanks	-	-	-	Х		-	-	Х	-	-	-	
For aggressive liquids	-	-		-	-	-		-	-	-	-	
For use in plastic tanks	-	-	2	X	-	-	2	X	-	-	-	
For use in mounting nozzles	-	-		-	Σ	K	]	X	-	-	Σ	ζ
In the event of condensate on tank ceiling	-			-	Σ	X	3	X	-	-	Σ	ζ
For high-viscosity liquids	Σ	ζ		-	Σ	Κ		-	Σ	ζ	Х	ζ
For high-viscosity conductive liquids	-	-		-	-	-		-	Σ	ζ	Х	Ĭ.

<sup>\*</sup> H3 = Thread height (important for calculating the exact probe length for process connections with a thread.)  $\rightarrow$   $\stackrel{\text{l}}{=}$  21 \*\* L2 must be >25 mm shorter than L1.

# Rope probes FTI52 (fully insulated)



#### Note

- The active probe length is always fully insulated (dimension L1).
- Total length of probe from sealing surface: L = L1 + L3
- All rope probes are prepared for tensioning in containers (tensioning weight / anchor hole)
  - In case of media < 1 mS/cm, appropriate measures must be taken, e.g. a metallic reference point or a metallic tank.
  - Back-and-forth swinging of the rope directly influences the switch point. The probe must therefore be tightened.
- Not suitable for agitator tanks, high-viscosity liquids and plastic tanks
- Thickness of rope insulation 0.75 mm
- Length tolerances L1, L3: <1 m: 0 to -10 mm, 1 to 3 m: 0 to -20 mm, 3 to 6 m: 0 to -30 mm, 6 to 12 m: 0 to -40 mm,

	Rod probe	Rope probe with clad Tri-Clamp	Rod probe with inactive length (uninsulated)	Rope probe with fully insulated inactive length
316L PTFE  PTFE  LIOU-FMISSERS-06-05-38-32-070	120 •	120	120 L1	120 LOV TEXT ST. 60 - 90 - TEXT 0 36 CO TEXT ST. 60 - 90 - 90 - 90 - 90 - 90 - 90 - 90 -
Total length (L)	420	10000	57012000	57011000
Active rope length (L1)	420	10000	42010000	42010000
Inactive length (L3)*			1002000	1501000
∅ Inactive length			22/43*	22**
Probe rope diameter		4	4	4
Ø Anchor weight	2	22	22	22
Ø Anchor hole		5	5	5
Tensile loading capacity (N) of probe rope at 20 C	2	00	200	200
For aggressive liquids		X		X
For use in mounting nozzles			Х	X
For conductive liquids > 100 $\mu$ S/cm			X	X
For non-conductive liquids $< 1 \mu S/cm$			X	X
In the event of condensate on tank ceiling			X	X
For high-viscosity liquids				

<sup>\*</sup> The arnothing value of the inactive length depends on the process connection selected, see product configurator ightarrow riangledown 44

<sup>\*\*</sup> Probe tube

#### Weight

Housing with process connection:

- F15, F16, F17, F13 approx. 4.0 kg
- T13 approx. 4.5 kg
- F27 approx. 5.5 kg
- + Flange weight
- + Probe rod Ø 10 mm: 0.5 kg/m,
- + Probe rod  $\varnothing$  22 mm: 0.8 kg/m
- + Probe rod  $\varnothing$  14 mm,  $\varnothing$  16 mm: 1.1 kg/m
- + Probe rope: 0.04 kg/m

#### Technical data: probe

#### Capacitance values of the probe

Basic capacitance: approx. 18 pF

#### Additional capacitance

Mount the probe at a minimum distance of 50 mm from a conductive container wall:

- Probe rod: approx. 1.3 pF/100 mm in air
- Probe rope: approx. 1.0 pF/100 mm in air

Fully insulated probe rod in water:

- Approx. 38 pF/100 mm (16 mm rod)
- Approx. 74 pF/100 mm (14 mm rod)
- Approx. 45 pF/100 mm (10 mm rod)
- Approx. 50 pF/100 mm (22 mm rod)

Insulated probe rope in water: approx. 19 pF/100 mm

Rod probe with ground tube:

- Insulated probe rod: approx. 6.4 pF/100 mm in air
- Insulated probe rod: approx. 38 pF/100 mm in water (16 mm rod)
- Insulated probe rod: approx. 45 pF/100 mm in water (10 mm rod)

#### Material

Material specifications as per AISI and DIN-EN.

#### In contact with the process

- Probe rod, ground tube, inactive length, tensioning weight for rope probe: 316L (1.4435)
- Probe rope: 316 (1.4401)
- Probe rod insulation: PFA or PTFE (FDA: 21 CFR 177.1550)
- Probe rope insulation: PFA or FEP (FDA: 21 CFR 177.1550)
- Process connection: 316L (1.4435 or 1.4404)
- Flat seal for process connection G ¾ or G 1: elastomer fiber, asbestos-free
- Sealing ring for process connection G ½, G ¾, G 1, G 1½:

Elastomer fiber, asbestos-free, resistant to lubricants, solvents, steam, weak acids and alkalis; to  $300\,\mathrm{C}$  and to  $100\,\mathrm{bar}$ 

#### Not in contact with the process

- Ground terminals on housing (exterior): 304 (1.4301)
- Nameplate on housing (exterior): 304 (1.4301)
- Cable glands
  - Housing F13, F15, F16, F17, F27: polyamide (PA)
  - With C, D, E, F, H, M, J, P, S, 1, 4, 5 approval ( $\rightarrow$   $\stackrel{\triangle}{=}$  44 ordering information): nickel-plated brass
  - Housing T13: nickel-plated brass
- Polyester housing F16: PBT-FR with cover made of PBT-FR or with sight glass made of PA12,
  - Cover seal: EPDM
  - Adhesive nameplate: polyester foil (PET)
  - Pressure compensation filter: PBT-GF20
- Stainless steel housing F15: 316L (1.4404)
  - Cover seal: silicone
  - Cover clamp: 304 (1.4301)
  - Pressure compensation filter: PBT-GF20, PA
- Aluminum housing F17/F13/T13: EN-AC-AlSi10Mg, plastic-coated,
  - Cover seal: EPDM
  - Cover clamp: nickel-plated brass
  - Pressure compensation filter: silicone (not T13)

- Stainless steel housing F27: 316L (1.4435)
  - Cover seal: FVMQ (optional: EPDM seal available as spare part)
  - Cover clamp: 316L (1.4435)

# **Input**

#### Measured variable

Measurement of change in capacitance between probe rod and tank wall or ground tube; depends on the level of a liquid.

Probe covered => high capacitance
Probe not covered => low capacitance

#### Measuring range

- Measuring frequency: 500 kHz
- Span:
  - $\Delta C = 5 \text{ to } 1600 \text{ pF}$
  - $-\Delta C = 5$  to 500 pF (with FEI58)
- Final capacitance: C<sub>E</sub> = max. 1600 pF
- Adjustable initial capacitance:
  - $-C_A = 5$  to 500 pF (range 1 = factory setting)
  - $-C_A = 5$  to 1600 pF (range 2; not with FEI58)
- The minimum change in capacitance for point level detection must be  $\geq 5$  pF.

### Minimum probe length for nonconductive media (<1µs/cm)

$$l_{min} = \Delta C_{min} / (C_s * [\epsilon r - 1])$$

 $l_{min}$  = Minimum probe length (m)

 $\Delta C_{\min} = 5 pF$ 

 $C_s$  = Probe capacitance in air  $\rightarrow$   $\stackrel{\triangle}{=}$  28 "Technical data: Probe"

 $\epsilon r$  = Dielectric constant e.g. oil = 2.0

#### Measuring conditions


### Notes!

- When installing in a nozzle, use inactive length (L3).
- Probes with active buildup compensation must be used for high-viscosity liquids that tend to form buildup.
- Fully insulated rod and rope probes have to be used for pump control (ΔS operation).
   The switch-on and switch-off points are determined by the empty and full calibration.
  - The maximum length depends on the probe used.

A 16 mm rod, for example, generates a capacitance of 380 pF/m in a conductive liquid.

With a maximum span of 1600 pF, this gives 1600 pF/380 pF per m = 4 m total length.

• In the case of nonconductive media: use a ground tube.



Dimensions mm (in)

Endress+Hauser 29

L00-FTI5xxxx-15-05-xx-xx-00

# Output

Switch behavior	Binary or $\Delta s$ operation (pump control, not with FEI58)				
Fail-safe mode	Minimum/maximum quiescent current safety can be switched at the electronic insert (for FEI53 and FEI57S only on the associated Nivotester: FTC325 3-WIRE, FTC325 PFM and FTC625				
	MIN = minimum safety: The output switches safety-oriented when the probe is uncovered (signal on alarm). For use for dry running protection and pump protection for example				
	MAX = maximum safety: The output switches safety-oriented when the probe is covered (signal on alarm). For use with overfill protection for example				
Switching delay	FEI51, FEI52, FEI54, FEI55 Can be adjusted incrementally at the electronic insert: 0.3 to 10 s				
	FEI53, FEI57S Depends on the connected Nivotester (transmitter): FTC325, FTC625, FTC470Z or FTC471Z				
	FEI58 Can be adjusted alternately at the electronic insert: 1 s / 5 s				
Galvanic isolation	FEI51, FEI52 between rod probe and power supply				
	FEI54: between rod probe, power supply and load				
	FEI53, FEI55, FEI57S, FEI58 see connected switching device (functional galvanic isolation in the electronic insert)				

# Electronic insert FEI51 (AC 2-wire)

#### Power supply

- Supply voltage: 19 to 253 V AC
- Power consumption: < 1.5 W
- Residual current consumption: < 3.8 mA
- Short-circuit protection
- Overvoltage category II


#### **Electrical connection**

#### Notes!

Always connect in series with a load! Check the following:

- the residual current consumption in blocked stat.
- that for low voltage:
  - the voltage drop across the load is such that the minimum terminal voltage at the electronic insert (19 V) when blocked is not undershot.
- the voltage drop across the electronics when switched through is observed (up to 12 V).
- that a relay cannot de-energize with holding power below 1 mA.
   If this is the case, a resistor should be connected parallel to the relay (RC module available on request).

When selecting the relay, pay attention to the holding power / rated power (see below: "Connectable load").



L00-FMI5xxxx-06-05-xx-en-071

### Signal on alarm

Safety mode	Level	Output signal	LEDs gn gn rd gn gn ye
MAX	104	L+ I <sub>L</sub> + 3	- <b>ॐ</b> • • • • - <b>☆</b> -
IVIAX		< 3,8 mA 1→ 3	<i>-</i> ∕⁄•••••
		L+ I <sub>L</sub> + 3	- <b>ÿ • • • •</b> - <b>ÿ</b> -
MIN		< 3,8 mA 1→ 3	-ÿ•••••
Maintenance required		I <sub>L</sub> / < 3,8 mA 1→ 3	-ÿ • -ÿ • • •
Instrument failu	ire L	< 3,8 mA 1→ 3	<b>ॐ•</b> ☆•••

BA300Fen017

#### Output signal

Output signal on power failure or in the event of damage to the sensor: < 3.8 mA

#### Connectable load

- For relays with a minimum holding power or rated power > 2.5 VA at 253 V AC (10 mA) or > 0.5 VA at 24 V AC (20 mA)
- Relays with a lower holding power or rated power can be operated by means of an RC module connected in parallel.
- For relays with a maximum holding power or rated power < 89 VA at 253 V AC or</li>
   8.4 VA at 24 V AC
- Voltage drop across FEI51 max. 12 V
- Residual current with blocked thyristor max. 3.8 mA
- Load switched directly into the power supply circuit via the thyristor.

# **Electronic insert FEI52 (DC PNP)**

# Power supply

- Supply voltage: 10 to 55 V DC
- Ripple: max. 1.7 V, 0 to 400 Hz
- Current consumption: < 20 mA
- Power consumption without load: max. 0.9 W
- Power consumption with full load (350 mA): 1.6 W
- Reverse polarity protection: yes
- Separation voltage: 3.7 kV
- Overvoltage category II


#### **Electrical connection**

#### Three-wire DC connection

Preferably in conjunction with programmable logic controllers (PLC),

DI modules in accordance with EN 61131-2.

Positive signal present at the switch output of the electronic system (PNP).



#### Output signal

Safety mode	Level	Output signal	LEDs gn gn rd gn gn ye	
MAX		L+	<b>→</b> • • • • <del>\</del>	I <sub>L</sub> = Load current (switched through) I <sub>R</sub> = Residual current
MAX		1 <del>-</del> 3	<i>ॐ</i> • • • • •	(blocked)
		L+ I <sub>L</sub> + 3	- <del>'</del> • • • • - <del>'</del> -	
MIN		13	<i>-</i> ∕⁄ • • • • •	
Maintenance required	-9	1	-ÿ •-ÿ • •	-\(\rightarrow\)- Lit
Instrument failu	ire L	I <sub>R</sub> 13	<b>ॐ •</b> ∳• • •	Flashes Unlit
			TI418Fen43	TI418F44

#### Signal on alarm

Output signal on power failure or in the event of device failure:  $I_R < 100 \mu A$ 

#### Connectable load

- Load switched via transistor and separate PNP connection, max. 55 V
- Load current max. 350 mA (cyclical overload and short-circuit protection)
- Residual current < 100 µA (with transistor blocked)
- $\bullet$  Capacitance load max. 0.5  $\mu F$  at 55 V; max. 1.0  $\mu F$  at 24 V
- Residual voltage < 3 V (for transistor switched through)

# Electronic insert FEI53 (3-wire)

# Power supply

- Supply voltage: 14.5 V DC
- Current consumption: < 15 mA
- Power consumption: max. 230 mW
- Reverse polarity protection: yes
- Separation voltage: 0.5 kV

#### **Electrical connection**


#### Three-wire DC connection

3 to 12 V signal

For connecting to the switching unit, Nivotester FTC325 3–WIRE from Endress+Hauser.

Switching between minimum/maximum Safety in the Nivotester FTC325 3-WIRE.

Point level adjustment directly at the Nivotester.



Output signal

Mode	Output signal	LEDs green red
Normal operation	312 V at terminal 3	- <b>&gt;</b>
Maintenance required *	312 V at terminal 3	- <b>j</b> - <b>j</b>
Instrument failure	< 2,7 V at terminal 3	- <b>ÿ</b> - <b>ÿ</b> -



Unlit

774.10

Signal on alarm

Voltage at terminal 3 vis-à-vis terminal 1: < 2.7 V

#### Connectable load

- Floating relay contacts in the connected switching unit Nivotester FTC325 3-WIRE
- For the contact load capacity, refer to the technical data of the switching device.

# Electronic insert FEI54 (AC/DC with relay output)

#### Power supply

Supply voltage: 19 to 253 V AC, 50/60 Hz or 19 to 55 V DC

Power consumption: max. 1.6 W
 Reverse polarity protection: yes
 Separation voltage: 3.7 kV

### Overvoltage category II

#### **Electrical connection**

# Universal current connection with relay output (DPDT)


Power supply: Please note the different voltage ranges for AC and DC. Alternating current.

#### Output:

When connecting an instrument with high inductance, provide a spark arrester to protect the relay contact.

A fine-wire fuse (depending on the load connected) protects the relay contact on short-circuiting.

Both relay contacts switch simultaneously.



Output signal

Safety mode	Level	Output signal	LEDs gn gn rd gn gn ye
MAX	10-1	3 4 5 6 7 8	<i>*</i> • • • • <i>*</i>
IVIAX		3 4 5 6 7 8	- <del>⁄</del>
		3 4 5 6 7 8	- <b>⁄</b> • • • • - <b>∕</b> ⁄
MIN		3 4 5 6 7 8	-
Maintenance required			-⁄⁄ • -⁄⁄ • • • • -⁄⁄ <sub>-</sub> Lit
Instrument failu	ire 4	3 4 5 6 7 8	-\(\sigma\) -\(\sigma\)-\(\sigma\)-\(\sigma\)-\(\sigma\)-\(\sigma\)
		345 678	TI418Fen48 TI418F49

#### Signal on alarm

Output signal on power failure or in the event of device failure: relay de-energized

#### Connectable load

- Loads switched via 2 floating changeover contacts (DPDT)
- I~ max. 6 A, U~ max. 253 V; P~ max. 1500 VA at  $\cos \varphi$  = 1, P~ max. 750 VA at  $\cos \varphi$  > 0.7
- I- max. 6 A to 30 V, I- max. 0.2 A to 125 V
- The following applies when connecting a functional low-voltage circuit with double isolation as per IEC 1010: Sum of voltages of relay output and power supply max. 300 V

34

<sup>\*</sup> See below "Connectable load"

# Electronic insert FEI55 (8/16 mA; SIL2/SIL3)

# Power supply


- Supply voltage: 11 to 36 V DC
- Power consumption: < 600 mW
- Reverse polarity protection: yes
- Separation voltage: 0.5 kV

#### **Electrical connection**

#### Two-wire connection for separate switching unit

For connecting to programmable logic controllers (PLC), AI modules 4 to 20 mA in accordance with EN 61131--2.

The point level signal is sent via an output signal jump from 8 mA to 16 mA.



# Output signal

Safety mode	Level	Output signal	LEDs gn gn rd gn gn ye
NAN		<sup>+</sup> 2 ~16 mA → 1	- <b>∕</b> ⁄ • • • • <b>∕</b> ⁄-
MAX		+ ~8 mA 1	- <del>⁄</del> ⁄⁄ • • • • •
MIN		+ ~16 mA → 1	- <del>'</del> • • • • <del>'</del>
		+ ~8 mA 1	- <del>'</del>
Maintenance required *		+ 8/16 mA 1	- <del>'</del> • - <del>'</del> • • •
Instrument failu	ire 4	+ < 3.6 mA 1	<i>-</i>

~16 mA = 16 mA ± 5 %

 $\sim 8 \text{ mA} = 8 \text{ mA} \pm 6 \%$ 

- Flashes

UnlitTI418F44

Signal on alarm

Output signal on power failure or in the event of device failure: < 3.6 mA


#### Connectable load

- U = Connection DC voltage:
- 11 to 36 V DC (non-hazardous area and Ex ia)
- 14.4 to 30 V DC (Ex d)
- $I_{max} = 16 \text{ mA}$

# **Electronic insert FEI57S (PFM)**

# Power supply

Supply voltage: 9.5 to 12.5 VDC Power consumption: < 150 mW Reverse polarity protection: yes Separation voltage: 0.5 kV



Frequency: 17 to 185 Hz


#### **Electrical connection**

#### Two-wire connection for separate switching unit

For connecting to switching units Nivotester FTC325, FTC625, FTC470Z, FTC471Z from Endress+Hauser.

PFM signal 17 to 185 Hz

Switching between minimum/maximum safety in the Nivotester.



Output signal

PFM 60 to 185 Hz (Endress+Hauser)

#### Signal on alarm

Mode	Output signal	LEDs green red	
Normal operation	60185 Hz 1 → 2	- <b>&gt;</b>	
Maintenance required *	60185 Hz 1 → 2	- <b>⁄a</b> - <b>⁄a</b>	-¤- Lit
Instrument failure	< 20 Hz 1 → 2	- <b>☆</b> - <b>☆</b> -	Flashes  Unlit

#### Connectable load

- Floating relay contacts in the connected switching unit Nivotester FTC325, FTC625, FTC470Z, FTC471Z
- For the contact load capacity, refer to the technical data of the switching device.

# Electronic insert FEI58 (NAMUR H-L edge)

# Power supply

- Power consumption: < 6 mW at I < 1 mA; < 38 mW at I = 2.2 to 4 mA
- Interface connection data: IEC 60947-5-6

#### **Electrical connection**

# Two-wire connection for separate switching unit

For connecting to isolating amplifiers as per NAMUR (IEC 60947-5-6), e.g. FXN421, FXN422, FTL325N, FTL375N from Endress+Hauser. Change in output signal from high to low current in event of point level detection.

## (H-L edge)

Additional function:


Test key on the electronic insert. Pressing the key interrupts the connection to the isolating amplifier.



Note!

In the case of Ex-d operation, the additional function can only be used if the housing is not exposed to an explosive atmosphere.

Connection to Multiplexer: set 3 s as the cycle time at least.



L00-FTL5xxxx-04-05-xx-en-00

# Output signal



Fail-safe mode	Level	Output signal	LEDs green yellow	
Max.		2.2 + 3.5 mA 2 1		->
iviax.		0.6 + 1.0 mA 2 1	->	•
	<b>ab</b>	2.2 + 3.5 mA 2 1	->	-\\.
Min.	<b>a</b>	0.6 + 1.0 mA 2	->	•
	1	1	L00-FTL5xxxx	04-05-xx-xx-0

## Signal on alarm

Output signal in the event of damage to the sensor: < 1.0 mA

# Connectable load

- See the technical data of the connected isolating amplifier as per IEC 60947-5-6 (NAMUR)
- Connection also to isolating amplifiers which have special safety circuits (I > 3.0 mA)

# Power supply

# **Electrical connection**

# **Connection compartment**

Six housings with the following protection classes are available:

Housing	Standard	Ex ia	Ex d	Gas-tight process seal
Polyester housing F16	Х	X	-	-
Stainless steel housing F15	X	X	-	-
Aluminum housing F17	X	X	-	-
Aluminum housing F13	Х	Х	X	Х
Stainless steel housing F27	X	X	X	Х
Aluminum housing T13 (with separate connection compartment)	X	Х	Х	X

## Connector

For the version with a connector M12, the housing does not have to be opened for connecting the signal line.

# PIN assignment for M12 connector

4 • 3 •	PIN	2-wire-electronic insert FEI55, FEI57, FEI58, FEI50H, FEI57C	3-wire-electronic insert FEI52, FEI53
	1	+	+
1 • 2 •	2	not used	not used
	3	-	-
L00-FTI5xxxx-04-06-xx-xx-015	4	ground	external load / signal

# Cable entry

- Cable gland: M20x1.5 (for Ex d only cable entry M20)
   Two cable glands included in scope of delivery.
- Cable entry: G 1/2, NPT 1/2 and NPT 3/4.

# **Performance characteristics**

Uncertainty: DIN 61298-2: max ±0.3%

Non-repeatability (reproducibility): DIN 61298-2: max.  $\pm 0.1 \%$ 

## Reference operating conditions

- Room temperature: +20 °C ±5 °C
- - $-\Delta C = 5...1600 \text{ pF}$
  - $-\Delta C = 5...500 \text{ pF (with FEI58)}$

## Switch-on behavior

When the power supply is switched on, the switching status of the outputs corresponds to the signal on alarm.

The correct switch condition is reached after max. 3 seconds.

## Ambient temperature effect

## **Electronic insert**

<0.06~% / 10~K related to the full scale value


## Separate housing

Capacitance change of connecting cable per meter 0.15 pF/10K

# **Human** interface

#### **Electronic inserts**

## FEI51, FEI52, FEI54, FEI55



Green LED 1 (6) ready for operation), red LED 3 (4) error indicated), yellow LED 6 (R switching state)


Function switch Function - key + key		Light emitting diodes (LED signals)							
position				Ф		4			<b>⇔</b>
7			+		<i>☆</i> -	<i>≱</i> ′	- <u>;</u> ;-	- ☆- - <b>☆</b> •	<b>☆</b> <b>≱</b>
				1 (green)	2 (green)	3 (red)	4 (green)	5 (green)	6 (yellow)
	Operation			Flashes	On	Flashes	On		On/off/
1				Operationa	(MIN-SIL)	(warning/	(MAX-SIL)		flashes
				l LED		alarm)			
	Restore	Press bot	h keys for	On	->	->	->	->	On/off/
	factory setting		rox.						flashes
		20	0 s						

Function switch	Function	- key	+ key	Light emitting diodes (LED signals)					
position				Ф		4			≎
7			+	∜ ⇒ • 1 (green)	<ul><li>☆</li><li>2 (green)</li></ul>	3 (red)	<ul><li></li><li></li><li>4 (green)</li></ul>	<ul><li>☆</li><li>→</li><li>5 (green)</li></ul>	6 (yellow)
	Empty calibration	Press		On	(3	( ( )	(3	- (3)	On/off/
2				(present)					flashes
	Full calibration		Press					On (present)	On/off/ flashes
	Reset: Calibration and switchpoint adjustment	app	h keys for orox. O s	On	->	->	->	->	On/off/ flashes
3 \( \begin{picture}( \times \) \\ \times \\ \	Switch point shift	Press for <	Press for >	On (2 pF)	Off (4 pF)	Off (8 pF)	Off (16 pF)	Off (32 pF)	On/off/ flashes
4	Measuring range	Press for <		<b>On</b> (500 pF)	<b>Off</b> (1600 pF)				On/off/ flashes
Δs	Two-point control $\Delta s$		Press once					On	On/off/ flashes
	buildup mode		Press twice				On	On	On/off/ flashes
5 T	Switching delay	Press for <	Press for >	Off (0.3 s)	<b>On</b> (1.5 s)	<b>Off</b> (5 s)	<b>Off</b> (10 s)		On/off/ flashes
6	Self-test (function test)	Press both l	xeys	Off (inactive)				Flashes (active)	On/off/ flashes
7	MIN-/MAX Fail-safe mode	Press for MIN	Press for MAX	Off (MIN)				On (MAX)	On/off/ flashes
	SIL mode* lock/unlock	Press both l			On (MIN-SIL)		On (MAX-SIL)		On/off/ flashes
8 1	Upload/download sensor DAT (EEPROM)	Press for download	Press for upload	Flashes (download )				Flashes (upload)	On/off/ flashes

<sup>\*</sup> Only in conjunction with FEI55 electronic insert (SIL).

# **Electronic inserts**

# FEI53, FEI57S




 $\textit{Green LED ($\Phi$ ready for operation), red LED ($\frac{1}{3}$ error indicated)}$ 

DIP sw	itch	Function
A	В	
Α	Standard	Standard <sup>1)</sup> : If the measuring range is exceeded <b>no</b> alarm is output.
A	Ф	印: If the measuring range is exceeded <b>an</b> alarm is output.
В	0500pF	Measuring range: The measuring range is between 0 and 500 pF Span: The span is between 5 and 500 pF.
В	01600pF	Measuring range: The measuring range is between 0 and 1600 pF Span: The span is between 5 and 1600 pF.

# Electronic insert

# FEI58



 $\textit{Green LED 1 ($\Phi$ ready for operation), red LED 2 ($\P$ error indicated), yellow LED 3 ($R$ switching state)}$ 

DIF	switches (C, D, E, F)	Function
D		The probe is covered during calibration.
		The probe is uncovered during calibration.
D	<u></u>	
Е	△C I	Switchpoint adjustment: 10 pF
Е	△C □□□□	Switchpoint adjustment: 2 pF
F	ΔΤ	Switching delay: 5 s
F	∆T □□□	Switching delay: 1 s
G	MIN	Fail-safe mode: MIN The output switches safety-oriented when the probe is uncovered (signal on alarm). For use for dry running protection and pump protection for example
G	MAX	Fail-safe mode: MAX The output switches safety-oriented when the probe is covered (signal on alarm). For use with overfill protection for example

Key			Function
Α	В	С	
X			Display diagnostic code
	Х		Display calibration situation
Х	Х		Perform calibration (during operation)
Х	Х		Delete calibration points (during startup)
		Х	Test key $ oldsymbol{\mathfrak{D}} $ , (disconnects the transmitter from the switching unit)

# Certificates and approvals

# CE mark The measuring system meets the legal requirements of the applicable EC quidelines. These are listed in the corresponding EC Declaration of Conformity together with the standards applied. Endress+Hauser confirms successful testing of the device by affixing to it the CE mark. RoHS The measuring system complies with the substance restrictions of the Restriction on Hazardous Substances Directive 2011/65/EU (RoHS 2). **RCM-Tick marking** The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products are labelled with the RCM- Tick marking on the name plate. Ex approval ATEX IECEx CSA FM NEPSI

## **EAC** conformity

The measuring system meets the legal requirements of the applicable EAC guidelines. These are listed in the corresponding EAC Declaration of Conformity together with the standards applied. Endress+Hauser confirms successful testing of the device by affixing to it the EAC mark.

# Other standards and quidelines

#### EN 60529

INMETROEAC

See "Certificates"  $\rightarrow = 45$ .

Degrees of protection by housing (IP code)

#### EN 61010

Protection measures for electrical equipment for measurement, control, regulation and laboratory procedures

### EN 61326

Interference emission (Class B equipment), interference immunity (Annex A - Industrial).

#### NAMUR

Association for Standards for Control and Regulation in the Chemical Industry

## IEC 61508

Functional safety

## Additional approvals

- TSE Certificate of Suitability (FMI51)

The following applies to wetted device components:

- They do not contain any materials derived from animals.
- No additives or operating materials derived from animals are used in production or processing.

Note

The wetted device components are listed in the "Mechanical construction" ( $\rightarrow \stackrel{\triangle}{=} 19 \text{ ff}$ ).

■ AD2000

The wetted material (316L) corresponds to AD2000 - W0/W2

## CRN approval

Versions with a CRN approval (Canadian Registration Number) are listed in the corresponding registration documents. CRN-approved devices are labeled with registration number CRN 0F1988.7C on the nameplate. You can find further details on the maximum pressure values in the Download Area of the Endress+Hauser website.

# Pressure Equipment Directive 2014/68/EU (PED)

# Pressure equipment with allowable pressure $\leq$ 200 bar (2900 psi)

Pressure instruments with a flange and threaded boss that do not have a pressurized housing do not fall within the scope of the Pressure Equipment Directive, irrespective of the maximum allowable pressure.

#### Reasons

According to Article 2, point 5 of EU Directive 2014/68/EU, pressure accessories are defined as "devices with an operational function and having pressure-bearing housings". If a pressure instrument does not have a pressure-bearing housing (no identifiable pressure chamber of its own), there is no pressure accessory present within the meaning of the Directive.

# Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser web site: www.endress.com → Choose your country → Products → Select measuring technology, software or components → Select product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product is opened.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

# Accessories

## Protective cover

For F13, F17 and F27 housing (without display)

Order number: 71040497

For F16 housing

Order number: 71127760

## Shortening kit for FTI52

Order number: 942901-0001

# Overvoltage protection HAW56x

Surge arrester for limiting overvoltage in signal lines and components.



## Note!

For detailed information about overvoltage protection please refer to the following documents::

- TIO1012K: HAW562 Overvoltage protective for installation on housing M20x1,5
- TI01013K: HAW569 Overvoltage protective for installation on housing in cabinet

## Weld-in adapter

All the weld-in adapters available are described in the document TI426F.

This is available in the Download Area of the Endress+Hauser web site: www.endress.com  $\rightarrow$  Download

# **Documentation**



Note!

This documentation is available on the product pages at www.endress.com

#### **Technical Information**

- Nivotester FTL325N TI00353F/00/en
- Nivotester FTL375N TI00361F/00/en
- EMC test procedures TI00241F/00/en

## **Operating Instructions**

 Liquicap M FTI51, FTI52 BA00299F/00/en

#### Certificates

## ATEX safety instructions

- Liquicap M FTI51, FTI52 ATEX II 1/2 G EEx ia IIC/IIB T3 to T6, II 1/2 D IP65 T 85 °C XA00327F/00/a3
- Liquicap M FTI51, FTI52 ATEX II 1/2 G Ex d [ia] IIC/IIB T3...T6, Ex de [ia Ga] IIC/IIB T3...T6 Ga/Gb, Ex iaD 20 Txx°C/Ex tD A21 IP6x Txx°C XA00328F/00/A3

#### **INMETRO** safety instructions

- Liquicap M FMI51, FMI52 Ex d [ia Ga] IIC/IIB T3...T6 Ga/Gb; Ex de [ia Ga] IIC T3...T6 Ga/Gb XA01171F/00/A3
- Liquicap M FMI51, FMI52 Ex ia IIC/IIB T3...T6 Ga/Gb; Ex ia IIIC T90°C Da/Db IP65 XA01172F/00/A3

## **NEPSI** safety instructions

- Liquicap M FTI51, FTI52
   Ex ia IIC/IIB T3 to T6 Ga/Gb
   XA00417F/00/a3
- Liquicap M FTI51, FTI52 EEx d [ia] IIC/IIB T3/T4/T6 Ga/Gb, Ex de ia IIC/IIB T3/T4/T6 XA00418F/00/a3

## Overfill protection DIBt (WHG)

 Liquicap M FTI51, FTI52 ZE00268F/00/en

# Functional safety (SIL2/SIL3)

Liquicap M FTI51, FTI52 SD00278F/00/en

# Control Drawings (FM and CSA)

- Liquicap M FTI51, FTI52 CSA: ZD00221F/00/en
- Liquicap M FTI51, FTI52 FM: ZD00220F/00/en



www.addresses.endress.com

