Services

Technical Information **Proline Promass H 100**

Coriolis flowmeter



The chemically resistant single-tube flowmeter with an ultra-compact transmitter

Application

- Measuring principle operates independently of physical fluid properties such as viscosity or density
- Highly accurate measurement of liquids and gases in applications requiring excellent corrosion resistance

Device properties

- Measuring tube made of tantalum and zirconium
- Nominal diameter: DN 8 to 50 (³/₈ to 2")
- Medium temperature up to +200 $^{\circ}$ C (+392 $^{\circ}$ F)
- Robust, ultra-compact transmitter housing
- Highest degree of protection: IP69K
- Local display available

Your benefits

- Maximum safety for chemically aggressive fluids corrosion-resistant wetted parts
- Fewer process measuring points multivariable measurement (flow, density, temperature)
- Space-saving installation no inlet/outlet run needs
- Space-saving transmitter full functionality on smallest footprint
- Time-saving local operation without additional software and hardware integrated web server
- Integrated verification Heartbeat Technology™



People for Process Automation

Table of contents

Document information	
Symbols used	4
Function and system design	5
Measuring principle	
Measuring system	
Equipment architecture	
Safety	
Surety	,
Input	8
Measured variable	
Measuring range	
Operable flow range	
Input signal	9
Output	9
Output signal	
Signal on alarm	11
Ex connection data	12
Low flow cut off	13
Galvanic isolation	13
Protocol-specific data	13
Deuron cumply	23
Power supply	23
Pin assignment, device plug	30
Supply voltage	32
Power consumption	33
Current consumption	33
Power supply failure	33
Electrical connection	34
Potential equalization	39
Terminals	39
Cable entries	39
Cable specification	39
Performance characteristics	41
Reference operating conditions	41
Maximum measured error	41
Repeatability	43
Response time	43
Influence of ambient temperature	43
Influence of medium temperature	43
Influence of medium pressure	44
Design fundamentals	44
Installation	45
Mounting location	4 5
Orientation	45
Inlet and outlet runs	40
Special mounting instructions	47
Mounting Safety Barrier Promass 100	47
Facine wat	/ -
Environment	47
Ambient temperature range	47
Storage temperature	50 50
	50

Degree of protection	50 50
Shock resistance	50 50
Interior cleaning	50
Electromagnetic compatibility (EMC)	50
	20
Process	51
Medium temperature range	51
Density	51
Pressure-temperature ratings	51
Secondary containment pressure rating	52
Flow limit	52 53
Pressure loss	53 53
Thermal insulation	رر 53
Heating	54
Vibrations	54
Mechanical construction	55
Dimensions in SI units	55
Dimensions in US units	60
Weight	64
Materials	65
Process connections	66
Surface roughness	66
Operability	66
Operating concept	66
Local display	67
Remote operation	67
Service interface	69
Certificates and approvals	71
CE mark	71
C-Tick symbol	71
Ex approval	72 72
	17.
Certification PROFIBUS	
Certification PROFIBUS	72
Certification PROFIBUS	72 73
Certification PROFIBUS	72 73 73
Certification PROFIBUS Certification PROFINET	72 73
Certification PROFIBUS	72 73 73 73
Certification PROFIBUS Certification PROFINET	72 73 73 73
Certification PROFIBUS	72 73 73 73 73 74
Certification PROFIBUS	72 73 73 73 73 74
Certification PROFIBUS Certification PROFINET EtherNet/IP certification Modbus RS485 certification Pressure Equipment Directive Other standards and guidelines Ordering information Application packages Heartbeat Technology	72 73 73 73 73 74 74
Certification PROFIBUS	72 73 73 73 73 74
Certification PROFIBUS Certification PROFINET EtherNet/IP certification Modbus RS485 certification Pressure Equipment Directive Other standards and guidelines Ordering information Heartbeat Technology Concentration	72 73 73 73 73 74 74
Certification PROFIBUSCertification PROFINETEtherNet/IP certificationModbus RS485 certificationPressure Equipment DirectiveOther standards and guidelinesOrdering informationApplication packagesHeartbeat TechnologyConcentration	72 73 73 73 73 73 74 74 74 74
Certification PROFIBUSCertification PROFINETEtherNet/IP certificationModbus RS485 certificationPressure Equipment DirectiveOther standards and guidelinesOrdering informationApplication packagesHeartbeat TechnologyConcentrationAccessoriesDevice-specific accessories	72 73 73 73 73 74 74 74 75 75
Certification PROFIBUSCertification PROFINETEtherNet/IP certificationModbus RS485 certificationPressure Equipment DirectiveOther standards and guidelinesOrdering informationApplication packagesHeartbeat TechnologyConcentration	72 73 73 73 73 73 74 74 75 75
Certification PROFIBUSCertification PROFINETEtherNet/IP certificationModbus RS485 certificationPressure Equipment DirectiveOther standards and guidelinesOrdering informationApplication packagesHeartbeat TechnologyConcentrationDevice-specific accessoriesCommunication-specific accessories	72 73 73 73 73 74 74 74 75 75 75

Supplementary documentation	77
Standard documentation	77
Supplementary device-dependent documentation	77

Document information

Symbols used

Electrical symbols

Symbol	Meaning	Symbol	Meaning
	Direct current	\sim	Alternating current
R	Direct current and alternating current	<u> </u>	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
Ð	Protective ground connection A terminal which must be connected to ground prior to establishing any other connections.	Ą	Equipotential connection A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice.

Symbols for certain types of information

Symbol	Meaning
\checkmark	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
\mathbf{X}	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
Ĩ	Reference to documentation
	Reference to page
	Reference to graphic
	Visual inspection


Symbols in graphics

Symbol	Meaning	Symbol	Meaning
1, 2, 3,	Item numbers	1. , 2. , 3	Series of steps
A, B, C,	Views	A-A, B-B, C-C,	Sections
EX	Hazardous area	×	Safe area (non-hazardous area)
≈➡	Flow direction		


Function and system design

Measuring principle	The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present in a system when both translational and rotational movements are superimposed.
	$F_c = 2 \cdot \Delta m (v \cdot \omega)$
	$F_c =$ Coriolis force
	$\Delta m = moving mass$
	$\omega = \text{ rotational velocity}$
	v = radial velocity in rotating or oscillating system
	The amplitude of the Coriolis force depends on the moving mass Δm , its velocity v in the system and thus on the mass flow. Instead of a constant rotational velocity ω , the sensor uses oscillation.
	 In the sensor, an oscillation is produced in the measuring tube. The Coriolis forces produced at the measuring tube cause a phase shift in the tube oscillations (see illustration): If there is zero flow (i.e. when the fluid stands still), the oscillation measured at points A and B ha the same phase (no phase difference). Mass flow causes deceleration of the oscillation at the inlet of the tubes (2) and acceleration at the outlet (3).
	The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube oscillations at the inlet and outlet. System balance is created by exciting an eccentrically arranged swinging mass to antiphase oscillation. The measuring principle operates independently os temperature, pressure, viscosity, conductivity and flow profile.
	Density measurement The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising measuring tube and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. Resonance frequency is thus a function of medium density. The microprocessor utilizes this relationship to obtain a density signal.
	Volume measurement Together with the measured mass flow, this is used to calculate the volume flow.
	Temperature measurement The temperature of the measuring tube is determined in order to calculate the compensation factor due to temperature effects. This signal corresponds to the process temperature and is also available as an output signal.
Measuring system	The device consists of a transmitter and a sensor. If a device with Modbus RS485 intrinsically safe is ordered, the Safety Barrier Promass 100 is part of the scope of supply and must be implemented to operate the device.
	The device is available as a compact version:


Transmitter




Sensor



Safety Barrier Promass 100



Equipment architecture



- I Possibilities for integrating measuring devices into a system
- 1 Automation system (e.g. PLC)
- 2 EtherNet/IP
- 3 PROFIBUS DP
- 4 Modbus RS485
- 5 4-20 mA HART, pulse/frequency/switch output
- 6 Safety Barrier Promass 100
- 7 Modbus RS485 intrinsically safe
- 8 Non-hazardous area
- 9 Non-hazardous area and Zone 2/Div. 2
- 10 Intrinsically safe area and Zone 1/Div. 1

Safety

IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

Input

Measured variable	Direct measured variables
	Mass flowDensity
	DensityTemperature

Calculated measured variables

- Volume flow
- Corrected volume flow
- Reference density

Measuring range

Measuring ranges for liquids

DN		Measuring range full scale values $\dot{m}_{min(F)}$ to $\dot{m}_{max(F)}$	
[mm]	[in]	[kg/h]	[lb/min]
8	3⁄8	0 to 2 000	0 to 73.50
15	1/2	0 to 6 500	0 to 238.9
25	1	0 to 18000	0 to 661.5
40	11/2	0 to 45 000	0 to 1654
50	2	0 to 70 000	0 to 2 573

Measuring ranges for gases

Measuring ranges only valid for Promass H with tantalum 2.5W.

The full scale values depend on the density of the gas and can be calculated with the formula below: $\dot{m}_{max(G)} = \dot{m}_{max(F)} \cdot \rho_G$: x

m _{max(G)}	Maximum full scale value for gas [kg/h]	
m _{max(F)}	Maximum full scale value for liquid [kg/h]	
$\dot{m}_{\max(G)} < \dot{m}_{\max(F)}$	$\dot{m}_{max(G)}$ can never be greater than $\dot{m}_{max(F)}$	
ρ _G	Gas density in [kg/m ³] at operating conditions	

D	N	х
[mm]	[in]	[kg/m ³]
8	3⁄8	60
15	1/2	80
25	1	90
40	1½	90
50	2	90



To calculate the measuring range, use the *Applicator* sizing tool $\rightarrow \square 76$

Recommended measuring range

"Flow limit" section $\rightarrow \square 52$

Operable flow range

Over 1000 : 1.

Flow rates above the preset full scale value are not overridden by the electronics unit, with the result that the totalizer values are registered correctly.

Input signal	External measured values
	 To increase the accuracy of certain measured variables or to calculate the corrected volume flow for gases, the automation system can continuously write different measured values to the measuring device: Operating pressure to increase accuracy (Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S) Medium temperature to increase accuracy (e.g. iTEMP) Reference density for calculating the corrected volume flow for gases
	Yarious pressure transmitters and temperature measuring devices can be ordered from Endress +Hauser: see "Accessories" section → 🗎 77
	It is recommended to read in external measured values to calculate the following measured variables: Mass flow Corrected volume flow
	HART protocol
	The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions: • HART protocol • Burst mode
	Digital communication
	The measured values can be written from the automation system to the measuring via:

- PROFIBUS DPModbus RS485
- EtherNet/IP
- PROFINET
- FROFINEI

Output

Output signal

Current output

	· · · · · · · · · · · · · · · · · · ·
Current output	4-20 mA HART (active)
Maximum output values	 DC 24 V (no flow) 22.5 mA
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Adjustable: 0.07 to 999 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature The range of options increases if the measuring device has one or more application packages.

Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	 DC 30 V 25 mA
Voltage drop	For 25 mA: ≤ DC 2 V
Pulse output	

Pulse width	Adjustable: 0.05 to 2 000 ms
Maximum pulse rate	10 000 Impulse/s
Pulse value	Adjustable
Assignable measured variables	Mass flowVolume flowCorrected volume flow
Frequency output	
Output frequency	Adjustable: 0 to 10 000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature Image of options increases if the measuring device has one or more application packages.
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	 Off On Diagnostic behavior Limit value Mass flow Volume flow Corrected volume flow Density Reference density Temperature Totalizer 1-3 Flow direction monitoring Status Partially filled pipe detection Low flow cut off The range of options increases if the measuring device has one or more application packages.

PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud

Modbus RS485

Physical interface	In accordance with EIA/TIA-485-A standard
Terminating resistor	 For device version used in non-hazardous areas or Zone 2/Div. 2: integrated and can be activated via DIP switches on the transmitter electronics module For device version used in intrinsically safe areas: integrated and can be activated via DIP switches on the Safety Barrier Promass 100

EtherNet/IP

Standards In accordance with IEEE 802.5

PROFINET

Standards	In accordance with IEEE 802.3
-----------	-------------------------------

Signal on alarm

Depending on the interface, failure information is displayed as follows:

Current output

Failure mode	Choose from: • 4 to 20 mA in accordance with NAMUR recommendation NE 43 • 4 to 20 mA in accordance with US • Min. value: 3.59 mA • Max. value: 22.5 mA • Freely definable value between: 3.59 to 22.5 mA • Actual value
	Last valid value

HART

Device diagnostics	Device condition can be read out via HART Command 48
--------------------	--

Pulse/frequency/switch output

Pulse output	
Failure mode	Choose from: • Actual value • No pulses
Frequency output	
Failure mode	Choose from: • Actual value • 0 Hz • Defined value: 0 to 12 500 Hz
Switch output	
Failure mode	Choose from: • Current status • Open • Closed

PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

Modbus RS485

Failure mode	Choose from:
	 NaN value instead of current value
	 Last valid value

EtherNet/IP

Device diagnostics	Device condition can be read out in Input Assembly

PROFINET

In accordance with "Application Layer protocol for decentral device periphery and distributed automation", version 2.3

Local display

Plain text display With information on cause and remedial measures	
Backlight Red backlighting indicates a device error.	



Status signal as per NAMUR recommendation NE 107

Operating tool

- Via digital communication:
 - HART protocol
 - PROFIBUS DP
 - Modbus RS485
 - EtherNet/IP
 - PROFINET
- Via service interface
- Via Web server

Plain text display	With information on cause and remedial measures
--------------------	---

Additional information on remote operation $\rightarrow \cong 67$

Web browser

Plain text display	With information on cause and remedial measures
--------------------	---

Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes	
	The following information is displayed depending on the device version:	
	 Supply voltage active 	
	 Data transmission active 	
	 Device alarm/error has occurred 	
	 EtherNet/IP network available 	
	 EtherNet/IP connection established 	
	 PROFINET network available 	
	 PROFINET connection established 	
	 PROFINET blinking feature 	

Ex connection data

These values only apply for the following device version:

Order code for "Output", option M "Modbus RS485", for use in intrinsically safe areas

Safety Barrier Promass 100

Safety-related values

Terminal numbers			
Supply voltage		Signal transmission	
2 (L-) 1 (L+) 26 (A) 27 (B		27 (B)	
U _{nom} = DC 24 V U _{max} = AC 260 V		U _{nom} = DC 5 V U _{max} = AC 260 V	

Intrinsically safe values

Terminal numbers				
Supply voltage		Signal transmission		
	20 (L-) 10 (L+) 62 (A) 72 (B)			
$\begin{array}{c} U_{o}=16.24 \ V\\ I_{o}=623 \ mA\\ P_{o}=2.45 \ W\\ \\ With \ IIC \ ^{1)}: L_{o}=92.8 \ \mu\text{H}, \ C_{o}=0.433 \ \mu\text{F}, \ L_{o}/R_{o}=14.6 \ \mu\text{H}/\Omega\\ \\ With \ IIB \ ^{1)}: L_{o}=372 \ \mu\text{H}, \ C_{o}=2.57 \ \mu\text{F}, \ L_{o}/R_{o}=58.3 \ \mu\text{H}/\Omega \end{array}$				
For an overview and for information on the interdependencies between the gas group - sensor - nominal diameter, see the "Safety Instructions" (XA) document for the measuring device				

1) The gas group depends on the sensor and nominal diameter.

Transmitter

Intrinsically safe values

Order code for	Terminal numbers			
"Approval"	Supply voltage		Signal transmission	
	20 (L-)	10 (L+)	62 (A)	72 (B)
 Option BM: ATEX II2G + IECEx Z1 Ex ia, II2D Ex tb Option BO: ATEX II1/2G + IECEx Z0/Z1 Ex ia, II2D Option BQ: ATEX II1/2G + IECEx Z0/Z1 Ex ia Option BU: ATEX II2G + IECEx Z1 Ex ia Option C2: CSA C/US IS Cl. I, II, III Div. 1 Option 85: ATEX II2G + IECEx Z1 Ex ia + CSA C/US IS Cl. I, II, III Div. 1 		$\begin{array}{c} U_i = 1\\ I_i = 62\\ P_i = 2\\ L_i =\\ C_i = \end{array}$	23 mA .45 W 0 µH	
For an overview and for information on the interd diameter, see the "Safety Instructions" (XA) docum				or - nomina

Low flow cut off	The switch points for low flow cut off are user-selectable.		
Galvanic isolation	The following connections are galvanically isolated from each other: • Outputs • Power supply		
Protocol-specific data HART			
	Manufacturer ID 0x11		
	Device type ID	0x4A	
	HART protocol revision 7		
	Device description files (DTM, DD)Information and files under: www.endress.com		
	HART load	Min. 250 Ω	

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.	
	Measured variables for PV (primary dynamic variable) Mass flow Volume flow Corrected volume flow Density Reference density Temperature 	
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable) • Mass flow • Volume flow • Corrected volume flow • Density • Reference density • Temperature • Totalizer 1 • Totalizer 2 • Totalizer 3 Image of options increases if the measuring device has one or mor application packages.	
	 Heartbeat Technology Application Package Additional measured variables are available with the Heartbeat Technology application package: Carrier pipe temperature Oscillation amplitude 0 	
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned. A maximum of 8 device variables can be transmitted: 0 = mass flow 1 = volume flow 2 = corrected volume flow 3 = density 4 = reference density 5 = temperature 6 = totalizer 1 7 = totalizer 2 8 = totalizer 3 13 = target mass flow 15 = concentration 	

PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x1561
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: • www.endress.com On the product page for the device: Documents/Software → Device drivers • www.profibus.org

Output values (from measuring device to automation system)	Analog input 1 to 8 Mass flow Volume flow Corrected volume flow Target mass flow Carrier mass flow Carrier mass flow Density Reference density Concentration Temperature Carrier pipe temperature Carrier pipe temperature Electronic temperature Oscillation frequency Oscillation amplitude Frequency fluctuation Oscillation damping Tube damping fluctuation Signal asymmetry Exciter current Digital input 1 to 2 Partially filled pipe detection Low flow cut off	
	Totalizer 1 to 3 Mass flow Volume flow Corrected volume flow	
Input values (from automation system to measuring device)	Analog output 1 to 3 (fixed assignment) Pressure Temperature Reference density	
	 Digital output 1 to 3 (fixed assignment) Digital output 1: switch positive zero return on/off Digital output 2: perform zero point adjustment Digital output 3: switch switch output on/off 	
	Totalizer 1 to 3 • Totalize • Reset and hold • Preset and hold • Stop • Operating mode configuration: - Net flow total - Forward flow total - Reverse flow total	
Supported functions	 Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur 	
Configuration of the device address	 DIP switches on the I/O electronics module Via operating tools (e.g. FieldCare) 	

Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1		
Device type	Slave		
Slave address range	1 to 247		
Broadcast address range	0		

Function codes	 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers 	
Broadcast messages	Supported by the following function codes: 06: Write single registers 16: Write multiple registers 23: Read/write multiple registers 	
Supported baud rate	 1200 BAUD 2400 BAUD 4800 BAUD 9600 BAUD 19200 BAUD 38400 BAUD 57 600 BAUD 115200 BAUD 	
Data transfer mode	ASCII RTU	
Data access	Each device parameter can be accessed via Modbus RS485.	

EtherNet/IP

Protocol	The CIP Networks Library Volume 1: Common Industrial ProtocolThe CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP		
Communication type	10Base-T100Base-TX		
Device profile	Generic device (product type: 0x2B)		
Manufacturer ID	0x49E		
Device type ID	0x104A		
Baud rates	Automatic $^{10}\!\!\!/_{100}$ Mbit with half-duplex and full-duplex detection		
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs		
Supported CIP connections	Max. 3 connections		
Explicit connections	Max. 6 connections		
I/O connections	Max. 6 connections (scanner)		
Configuration options for measuring device	 DIP switches on the electronics module for IP addressing Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser Electronic Data Sheet (EDS) integrated in the measuring device 		
Configuration of the EtherNet interface	 Speed: 10 MBit, 100 MBit, auto (factory setting) Duplex: half-duplex, full-duplex, auto (factory setting) 		
Configuration of the device address	 DIP switches on the electronics module for IP addressing (last octet) DHCP Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser EtherNet/IP tools, e.g. RSLinx (Rockwell Automation) 		
Device Level Ring (DLR)	No		

RPI	5 ms to 10 s (factory setting: 20 ms)			
Exclusive Owner Multicast		Instance	Size [byte]	
	Instance configuration:	0x68	398	
	$O \rightarrow T$ configuration:	0x66	64	
	$T \rightarrow O$ configuration:	0x64	44	
Exclusive Owner Multicast		Instance	Size [byte]	
	Instance configuration:	0x69	-	
	$O \rightarrow T$ configuration:	0x66	64	
	$T \rightarrow O$ configuration:	0x64	44	
Input only Multicast		Instance	Size [byte]	
	Instance configuration:	0x68	398	
	$O \rightarrow T$ configuration:	0xC7	-	
	$T \rightarrow O$ configuration:	0x64	44	
input only Multicast		Instance	Size [byte]	
	Instance configuration:	0x69	-	
	$O \rightarrow T$ configuration:	0xC7	-	
	$T \rightarrow O$ configuration:	0x64	44	
	 Reference density Temperature Totalizer 1 Totalizer 2 			
	• Totalizer 3			
Configurable Input	Totalizer 3			
Configurable Input RPI	Totalizer 3 5 ms to 10 s (factory setting: 2	20 ms)	1	
RPI	5 ms to 10 s (factory setting: 2	20 ms) Instance	Size [byte]	
	5 ms to 10 s (factory setting: 2 Instance configuration:		Size [byte] 398	
RPI	5 ms to 10 s (factory setting: 2 Instance configuration: $O \rightarrow T$ configuration:	Instance		
RPI	5 ms to 10 s (factory setting: 2 Instance configuration:	Instance 0x68	398	
RPI	5 ms to 10 s (factory setting: 2 Instance configuration: $O \rightarrow T$ configuration: T $\rightarrow O$ configuration:	Instance 0x68 0x66	398 64	
RPI Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $O \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration:Instance configuration:	Instance 0x68 0x66 0x65	398 64 88	
RPI Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2 Instance configuration: $O \rightarrow T$ configuration: T $\rightarrow O$ configuration:	Instance 0x68 0x66 0x65 Instance	398 64 88 Size [byte]	
RPI Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $O \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration:Instance configuration:	Instance 0x68 0x66 0x65 Instance 0x69	398 64 88 Size [byte] -	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $O \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration:Instance configuration: $O \rightarrow T$ configuration: $O \rightarrow T$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66	398 64 88 Size [byte] - 64	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $O \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration:Instance configuration: $O \rightarrow T$ configuration: $O \rightarrow T$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65	398 64 88 Size [byte] - 64 88	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2 Instance configuration: $O \rightarrow T$ configuration: T $\rightarrow O$ configuration: Instance configuration: O $\rightarrow T$ configuration: O $\rightarrow T$ configuration: T $\rightarrow O$ configuration: O $\rightarrow T$ configuration: O $\rightarrow T$ configuration: T $\rightarrow O$ configuration: T $\rightarrow O$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65 Instance	398 64 88 Size [byte] - 64 88 Size [byte]	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $O \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration: $O \rightarrow T$ configuration: $O \rightarrow T$ configuration: $T \rightarrow O$ configuration: $T \rightarrow O$ configuration:Instance configuration:Instance configuration:Instance configuration:Instance configuration:Instance configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65 Instance 0x68	398 64 88 Size [byte] - 64 88 Size [byte]	
RPI Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration: $0 \rightarrow T$ configuration: 1 nstance configuration: $T \rightarrow O$ configuration: $1 \rightarrow 0$ configuration: $T \rightarrow 0$ configuration: 1 nstance configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x65 0x67	398 64 88 Size [byte] - 64 88 Size [byte] 398 -	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration: $0 \rightarrow T$ configuration: 1 nstance configuration: $T \rightarrow O$ configuration: $1 \rightarrow 0$ configuration: $T \rightarrow 0$ configuration: 1 nstance configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration:	Instance 0x68 0x66 0x65 Instance 0x66 0x65 Instance 0x65 0x65 0x65 0x65 0x65 0x65 0x68 0x67 0x65	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	5 ms to 10 s (factory setting: 2Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow O$ configuration:Instance configuration: $0 \rightarrow T$ configuration: 1 nstance configuration: $0 \rightarrow T$ configuration: $1 \rightarrow O$ configuration: $0 \rightarrow T$ configuration: 1 nstance configuration: $0 \rightarrow T$ configuration: $1 \rightarrow O$ configuration: $0 \rightarrow T$ configuration: $1 \rightarrow 0$ configuration: $1 \rightarrow 0$ configuration: $1 \rightarrow 0$ configuration: $1 \rightarrow 0$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x65 0x65 0x65 0x65 0x65 0x65 0x65 Instance 0x65 Instance 0x68 0x65 Instance	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88 Size [byte]	

Configurable Input Assembly	 Current device diagnostics Mass flow Volume flow Corrected volume flow Density Reference density Temperature Totalizer 1 Totalizer 2 Totalizer 3 The range of options increases if the measuring device has one or more application packages.
Fix Output	
Output Assembly	 Activation of reset totalizers 1-3 Activation of pressure compensation Activation of reference density compensation Activation of temperature compensation Reset totalizers 1-3 External pressure value Pressure unit External reference density Reference density unit External temperature Temperature unit
Configuration	
Configuration Assembly	Only the most common configurations are listed below. Software write protection Mass flow unit Mass unit Volume flow unit Volume flow unit Corrected volume flow unit Corrected volume flow unit Density unit Reference density unit Temperature unit Pressure unit Length Totalizer 1-3: Assignment Unit Measuring mode Failsafe mode

PROFINET

Protocol	"Application layer protocol for decentral device periphery and distributed automation", version 2.3
Conformity class	В
Communication type	100 MBit/s
Device profile	Application interface identifier 0xF600 Generic device
Manufacturer ID	0x11
Device type ID	0x844A
Device description files (GSD, DTM)	Information and files under: • www.endress.com On the product page for the device: Documents/Software → Device drivers • www.profibus.org
Baud rates	Automatic 100 Mbit/s with full-duplex detection

Cycle times	From 8 ms		
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs		
Supported connections	 1 x AR (Application Relation) 1 x Input CR (Communication Relation) 1 x Output CR (Communication Relation) 1 x Alarm CR (Communication Relation) 		
Configuration options for measuring device	 DIP switches on the electronics module, for device name assignment (last part) Manufacturer-specific software (FieldCare, DeviceCare) Web browser Device master file (GSD), can be read out via the integrated Web server of the measuring device 		
Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol 		
Output values (from measuring device to automation system)	Analog Input module (slot 1 to 14)Mass flowVolume flowCorrected volume flowTarget mass flowCarrier mass flowDensityReference densityConcentrationTemperatureCarrier pipe temperatureElectronic temperatureOscillation frequencyOscillation amplitudeFrequency fluctuationOscillation dampingTube damping fluctuationSignal asymmetryExciter current		
	Discrete Input module (slot 1 to 14) Empty pipe detection Low flow cut off Diagnostics Input module (slot 1 to 14) Last diagnostics Current diagnosis Totalizer 1 to 3 (slot 15 to 17)		
	 Mass flow Volume flow Corrected volume flow Heartbeat Verification module (fixed assignment) 		
	Verification status (slot 23) The range of options increases if the measuring device has one or more application packages.		

Input values (from automation system to measuring device)	Analog Output module (fixed assignment) External pressure (slot 18) External temperature (slot 19) External reference density (slot 20) Discrete Output module (fixed assignment) Activate/deactivate positive zero return (slot 21) Perform zero point adjustment (slot 22)
	Totalizer 1 to 3 (slot 15 to 17) Totalize Reset and hold Preset and hold Stop Operating mode configuration: Net flow total Forward flow total Reverse flow total
	Heartbeat Verification module (fixed assignment) Start verification (slot 23)
	The range of options increases if the measuring device has one or more application packages.
Supported functions	 Identification & Maintenance Simple device identification via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the onsite display for simple device identification and assignment

Administration of software options

Input/output value	Process variable	Category	Slot
Output value	Mass flow	Process variable	114
	Volume flow		
	Corrected volume flow		
	Density	_	
	Reference density	_	
	Temperature		
	Electronic temperature	_	
	Oscillation frequency		
	Frequency fluctuation		
	Oscillation damping		
	Oscillation frequency		
	Signal asymmetry		
	Exciter current		
	Empty pipe detection		
	Low flow cut off		
	Current device diagnostics	_	
	Previous device diagnostics		
Output value	Target mass flow	Concentration ¹⁾	114
	Carrier mass flow		
	Concentration		
Output value	Carrier pipe temperature	Heartbeat ²⁾	114

Input/output value	Process variable	Category	Slot
	Oscillation damping 1		
	Oscillation frequency 1		
	Oscillation amplitude 0		
	Oscillation amplitude 1		
	Frequency fluctuation 1		
	Tube damping fluctuation 1		
	Exciter current 1		
Input value	External density	Process monitoring	18
	External temperature		19
	External reference density		20
	Flow override		21
	Zero point adjustment		22
	Verification status	Heartbeat Verification ²⁾	23

Only available with the "Concentration" application package. Only available with the "Heartbeat" application package. 1) 2)


Startup configuration (NSU)	If startup configuration is enabled, the configuration of the most important device parameters is taken from the automation system and used.
(1450)	
	The following configuration is taken from the automation system: Management
	- Software revision
	- Write protection
	System units
	- Mass flow
	– Mass
	- Volume flow
	- Volume
	 Corrected volume flow
	 Corrected volume
	– Density
	 Reference density
	- Temperature
	- Pressure
	 Concentration application package
	- Coefficients A0 to A4
	- Coefficients B1 to B3
	 Sensor adjustment
	 Process param.
	 Damping (flow, density, temperature)
	– Flow override
	 Low flow cut off
	 Assign process variable
	- Switch-on/switch-off point
	 Pressure shock suppression
	 Empty pipe detection
	 Assign process variable
	– Limit values
	 Response time
	– Max. damping
	 Corrected volume flow calculation
	 External reference density
	 Fixed reference density
	 Reference temperature
	 Linear expansion coefficient
	 Square expansion coefficient
	 Measuring mode
	– Medium
	– Gas type
	 Reference sound velocity
	 Temperature coefficient sound velocity
	 External compensation
	 Pressure compensation
	 Pressure value
	 External pressure
	 Diagnostic settings
	 Diagnostic behavior for diverse diagnostic information

Startup configuration

Power supply

Terminal assignment

Overview: housing version and connection versions



- A Housing version: compact, aluminum coated
- *B* Housing version: compact, stainless
- C Housing version: ultra-compact, stainless
- 1 Connection version: 4-20 mA HART, pulse/frequency/switch output
- 1.1 Signal transmission: pulse/frequency/switch output
- 1.2 Signal transmission: 4-20 mA HART
- 1.3 Supply voltage
- 2 Connection version: Modbus RS485
- 2.1 Signal transmission
- 2.2 Supply voltage
- 3 Connection version: EtherNet/IP and PROFINET
- 3.1 Signal transmission
- 3.2 Supply voltage
- 4 Connection version: PROFIBUS DP
- 4.1 Signal transmission
- 4.2 Supply voltage

Transmitter

Connection version 4-20 mA HART with pulse/frequency/switch output

Order code for "Output", option ${\boldsymbol{B}}$

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.


	_	Possible options for order code
Outputs	Power supply	"Electrical connection"
Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ¹/₂" Option D: thread NPT ¹/₂"
Device plugs → 🗎 30	Terminals	 Option L: plug M12x1 + thread NPT ¹/₂" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ¹/₂" Option U: plug M12x1 + thread M20
Device plugs → 🗎 30	Device plugs → 🗎 30	Option Q : 2 x plug M12x1
	Device plugs → 🖺 30 Device plugs	TerminalsTerminalsDevice plugs $\rightarrow \square 30$ TerminalsDevice plugs $\rightarrow \square 30$ Device plugs $\rightarrow \square 30$

Order code for "Housing":

• Option A: compact, coated aluminum

• Option **B**: compact, stainless

• Option **C**: ultra-compact, stainless



☑ 2 Terminal assignment 4-20 mA HART with pulse/frequency/switch output

- 1 Power supply: DC 24 V
- 2 Output 1: 4-20 mA HART (active)
- *3 Output 2: pulse/frequency/switch output (passive)*

		Terminal number				
Order code for "Output"	Power supply		Output 1		Output 2	
	2 (L-)	1 (L+)	27 (-)	26 (+)	25 (-)	24 (+)
Option B	DC 2	24 V	4-20 mA H.	ART (active)	Pulse/frequ output (5
Order code for "Output": Option B : 4-20 mA HART with pulse/frequency/switch output						

PROFIBUS DP connection version

For use in the non-hazardous area and Zone 2/Div. 2.

Order code for "Output", option ${\boldsymbol L}$

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.


Order code for	Connection me	thods available	Dessible antions for order as de
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ¹/₂" Option D: thread NPT ¹/₂"
Options A, B	Device plugs → 🗎 30	Terminals	 Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🗎 30	Device plugs → 🖺 30	Option Q : 2 x plug M12x1

Order code for "Housing":

• Option A: compact, coated aluminum

• Option **B**: compact, stainless

• Option **C**: ultra-compact, stainless



- B 3 PROFIBUS DP terminal assignment
- 1 Power supply: DC 24 V
- 2 PROFIBUS DP

	Terminal number				
Order code for	Power supply		Output		
"Output"	2 (L-)	1 (L+)	26 (RxD/TxD-P)	27 (RxD/TxD- N)	
Option L	DC 24 V		В	А	
Order code for "Output":					

Option L: PROFIBUS DP, for use in non-hazardous areas and Zone 2/div. 2

Modbus RS485 connection version

For use in the non-hazardous area and Zone 2/Div. 2.

Order code for "Output", option ${\boldsymbol{M}}$


Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Onden er de fen	Connection me	thods available		
Order code for "Housing"	Output	Power supply	Possible options for order code "Electrical connection"	
Options A, B	Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ¹/₂" Option D: thread NPT ¹/₂" 	
Options A, B	Device plugs → 🗎 30	Terminals	 Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20 	
Options A, B, C	Device plugs → 🗎 30	Device plugs → 🗎 30	Option Q : 2 x plug M12x1	
Order code for "Housing":				

Order code for "Housing":

Option A: compact, coated aluminum

Option B: compact, stainless Option C: ultra-compact, stainless



€ 4 Modbus RS485 terminal assignment, connection version for use in non-hazardous areas and Zone 2/Div. 2

Power supply: DC 24 V 1

Modbus RS485 2

	Terminal number					
Order code for "Output"	Power supply 0		Out	put		
Culput	2 (L-)	1 (L+)	27 (B)	26 (A)		
Option M	DC 24 V Modbus RS485					
Order code for "Output": Option M Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2						

Modbus RS485 connection version

For use in the intrinsically safe area. Connection via Safety Barrier Promass 100.

Order code for "Output", option **M**

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.


Order code for	Connection me	thods available	Describle entriene for order code
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ¹/₂" Option D: thread NPT ¹/₂"
A, B, C		e plugs € 30	Option I: plug M12x1
Order code for "Hou		∃ 30	

Order code for "Housing":

• Option A: compact, coated aluminum

Option B: compact, stainless

• Option **C**: ultra-compact, stainless



E 5 Modbus RS485 terminal assignment, connection version for use in intrinsically safe areas (connection via Safety Barrier Promass 100)

- 1 Intrinsically safe power supply
- 2 Modbus RS485

Order code for "Output"	20 (L-)	10 (L+)	72 (B)	62 (A)
Option M	Intrinsically safe	e supply voltage	Modbus RS485	intrinsically safe
Order code for "Output":				

Option M: Modbus RS485, for use in intrinsically safe areas (connection via Safety Barrier Promass 100)


EtherNet/IP connection version

Order code for "Output", option N

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Dessible entions for order as de	
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"	
Options A, B	Device plugs → 🗎 30	Terminals	 Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20 	
Options A, B, C	Device plugs → 🗎 30	Device plugs → 🗎 30	Option Q : 2 x plug M12x1	
Order code for "Housing":				

Order code for 'Housing':
Option A: compact, coated aluminum
Option B: compact, stainless
Option C: ultra-compact, stainless



💽 6 EtherNet/IP terminal assignment

Power supply: DC 24 V 1

EtherNet/IP 2

	Terminal number				
Order code for "Output"	Power supply 2 (L-) 1 (L+)		Output		
			Device plug M12x1		
Option N	DC 24 V		EtherNet/IP		
Order code for "Output": Option N : EtherNet/IP					

PROFINET connection version

Order code for "Output", option **R**


Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Dessible entires for order and
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Device plugs → 🗎 30	Terminals	 Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🗎 30	Device plugs → 🗎 30	Option Q : 2 x plug M12x1

Order code for "Housing":

• Option A: compact, coated aluminum

Option B: compact, stainless
Option C: ultra-compact, stainless




₽ 7 PROFINET terminal assignment

Power supply: DC 24 V 1

PROFINET 2

	Terminal number			
Order code for "Output"	Power supply		Output	
	2 (L-)	1 (L+)	Device plug M12x1	
Option R	DC 24 V		PROFINET	
Order code for "Output": Option R : PROFINET	•			

Safety Barrier Promass 100



- EtherNet/IP \rightarrow 🗎 28
- PROFINET → 🗎 29

Supply voltage

For all connection versions except MODBUS RS485 intrinsically safe (device side)

P Device plug MODBUS RS485 intrinsically safe with supply voltage → 🗎 31


2	Pin		Assignment
	1	L+	DC 24 V
	2		Not assigned
	3		Not assigned
5	4	L-	DC 24 V
4 A0016809	5		Grounding/shielding
	Cod	ling	Plug/socket
А		ł	Plug

The following is recommended as a socket:

- Binder, series 763, part no. 79 3440 35 05
- Alternatively: Phoenix part no. 1669767 SAC-5P-M12MS
 - With the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output
 With the order code for "Output", option N: EtherNet/IP
- When using the device in a hazardous location: Use a suitably certified socket.

4-20 mA HART with pulse/frequency/switch output

Device plug for signal transmission (device side)



 Recommended plug: Binder, series 763, part no. 79 3439 12 05 **i**


• When using the device in a hazardous location, use a suitably certified plug.

PROFIBUS DP

-

For use in the non-hazardous area and Zone 2/Div. 2.

Device plug for signal transmission (device side)



i

Recommended plug: Binder, series 763, part no. 79 4449 20 05When using the device in a hazardous location, use a suitably certified plug.


MODBUS RS485

Device plug for signal transmission with supply voltage (device side), MODBUS RS485 (intrinsically safe)

2	Pin	Assignment		
	1	L+	Supply voltage, intrinsically safe	
	2	А	Modbus RS485 intrinsically safe	
	3	В	Moubus K3405 mumisically sale	
	4	L-	Supply voltage, intrinsically safe	
4 A0016809	5		Grounding/shielding	
	Coding		Plug/socket	
А		ł	Plug	

Recommended socket: Binder, series 763, part no. 79 3439 12 05
 When using the device in a hazardous location: Use a suitably certified socket.

Device plug for signal transmission (device side), MODBUS RS485 (not intrinsically safe) For use in the non-hazardous area and Zone 2/Div. 2.



Recommended plug: Binder, series 763, part no. 79 4449 20 05

• When using the device in a hazardous location, use a suitably certified plug.

EtherNet/IP

i

Device plug for signal transmission (device side)


2	Pin		Assignment
\sim	1	+	Тх
	2	+	Rx
	3	-	Тх
	4	-	Rx
4 Coding		ling	Plug/socket
	Ι)	Socket

Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q
- When using the device in a hazardous location, use a suitably certified plug.

PROFINET

Device plug for signal transmission (device side)



Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q
- When using the device in a hazardous location, use a suitably certified plug.

Supply voltage

The power unit must be tested to ensure it meets safety requirements (e.g. PELV, SELV).

Transmitter

For device version with communication type:

- HART, PROFIBUS DP, EtherNet/IP: DC 20 to 30 V
- Modbus RS485, device version:
 - For use in the non-hazardous area and Zone 2/Div. 2: DC 20 to 30 V
 - For use in the intrinsically safe area: power supply via Safety Barrier Promass 100

Safety Barrier Promass 100

DC 20 to 30 V

Transmitter

Power consumption

Order code for "Output"	Maximum Power consumption
Option B : 4-20 mA HART with pulse/frequency/switch output	3.5 W
Option L: PROFIBUS DP	3.5 W
Option M Modbus RS485, for use in non-hazardous areas and Zone 2/ Div. 2	3.5 W
Option M : Modbus RS485, for use in intrinsically safe areas	2.45 W
Option N: EtherNet/IP	3.5 W
Option R: PROFINET	3.5 W

Safety Barrier Promass 100

Order code for "Output"	Maximum Power consumption	
Option \mathbf{M} : Modbus RS485, for use in intrinsically safe areas	4.8 W	

Current consumption

Transmitter

Order code for "Output"	Maximum Current consumption	Maximum switch-on current	
Option B : 4-20mA HART, pul./freq./switch output	145 mA	18 A (< 0.125 ms)	
Option L: PROFIBUS DP	145 mA	18 A (< 0.125 ms)	
Option M Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2	90 mA	10 A (< 0.8 ms)	
Option M : Modbus RS485, for use in intrinsically safe areas	145 mA	16 A (< 0.4 ms)	
Option N : EtherNet/IP	145 mA	18 A (< 0.125 ms)	
Option R: PROFINET	145 mA	18 A (< 0.125 ms)	

Safety Barrier Promass 100


Order code for "Output"	Maximum Current consumption	Maximum switch-on current	
Option ${\bf M}$: Modbus RS485, for use in intrinsically safe areas	230 mA	10 A (< 0.8 ms)	

Power supply failure

- Totalizers stop at the last value measured.
- Depending on the device version, the configuration is retained in the device memory or in the plug-in memory (HistoROM DAT).
- Configuration is retained in the plug-in memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

Electrical connection

Connecting the transmitter



- A Housing version: compact, aluminum coated
- *B* Housing version: compact, stainless
- 1 Cable entry or device plug for signal transmission
- 2 Cable entry or device plug for supply voltage
- C Housing version: ultra-compact, stainless
- 3 Device plug for signal transmission
- 4 Device plug for supply voltage

■ Terminal assignment → 🗎 23

Pin assignment, device plug $\rightarrow \cong 30$


In the case of device versions with a connector, the transmitter housing does not need to be opened to connect the signal cable or power supply cable.

Connection examples

ŀ


ĭ

Current output 4-20 mA HART



- Connection example for 4-20 mA HART current output (active)
- 1 Automation system with current input (e.g. PLC)
- 2 Cable shield, observe cable specifications
- 3 Connection for HART operating devices
- 4 Resistor for HART communication ($\geq 250 \Omega$): observe maximum load
- 5 Analog display unit: observe maximum load
- 6 Transmitter


Pulse/frequency output



 10 Connection example for pulse/frequency output (passive)


- Automation system with pulse/frequency input (e.g. PLC) 1
- Power supply
- 2 3 Transmitter: observe input values $\rightarrow \implies 9$

Switch output



- 🖻 11 Connection example for switch output (passive)
- Automation system with switch input (e.g. PLC) 1
- 2 3 Power supply
- Transmitter: observe input values

PROFIBUS DP




I2 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Transmitter

If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

Modbus RS485


Modbus RS485, non-hazardous area and Zone 2/Div. 2



■ 13 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter


Modbus RS485 intrinsically safe



🖸 14 Connection example for Modbus RS485 intrinsically safe

- 1
- Control system (e.g. PLC) Cable shield, observe cable specifications 2
- 3 Safety Barrier Promass 100
- 4 5 Observe cable specifications
- Non-hazardous area
- 6 Non-hazardous area and Zone 2/Div. 2
- Intrinsically safe area 7
- 8 Transmitter


EtherNet/IP




🖻 15 Connection example for EtherNet/IP

- 1 Control system (e.g. PLC)
- Ethernet switch 2
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter


PROFINET





- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Connector
- 5 Transmitter

HART input



🖸 17 Connection example for HART input (burst mode) via current output (active)

- 1 Cable shield, observe cable specifications
- Resistor for HART communication ($\geq 250 \Omega$): observe maximum load 2
- 3 Connection for HART operating devices Analog display unit
- 4
- 5 Transmitter
- 6 Sensor for external measured variable

	$\begin{bmatrix} 1 & 2 & 3 & 4 & 5 \\ & 4 & 20 \text{ mA} \\ & 4 & 20 \text{ mA} \\ & & & & & & & & & & & \\ & & & & & & $				
	 I8 Connection example for HART input (master mode) via current output (active) Automation system with current input (e.g. PLC). Prerequisite: automation system with HART version 6, HART commands 113 and 114 can be processed. Cable shield, observe cable specifications Resistor for HART communication (≥ 250 Ω): observe maximum load Connection for HART operating devices Analog display unit Transmitter Sensor for external measured variable 				
Potential equalization	Requirements				
	No special measures for potential equalization are required.				
	 Please consider the following to ensure correct measurement: Same electrical potential for the fluid and sensor Company-internal grounding concepts For devices intended for use in hazardous locations, please observe the guidelines in the Ex documentation (XA). 				
Terminals	Transmitter Spring terminals for wire cross-sections0.5 to 2.5 mm ² (20 to 14 AWG)				
	Safety Barrier Promass 100 Plug-in screw terminals for wire cross-sections 0.5 to 2.5 mm^2 (20 to 14 AWG)				
Cable entries	 Cable gland: M20 × 1.5 with cable \$\varphi\$6 to 12 mm (0.24 to 0.47 in) Thread for cable entry: NPT ½" G ½" M20 				
	- NPT ¹ /2" - G ¹ /2"				
Cable specification	- NPT ½" - G ½"				
Cable specification	- NPT ½" - G ½" - M20				
Cable specification	 NPT ½" G ½" M20 Permitted temperature range -40 °C (-40 °F) to +80 °C (+176 °F) 				
Cable specification	 NPT ½" G ½" M20 Permitted temperature range -40 °C (-40 °F) to +80 °C (+176 °F) Minimum requirement: cable temperature range ≥ ambient temperature +20 K 				
Cable specification	 NPT ½" G ½" M20 Permitted temperature range -40 °C (-40 °F) to +80 °C (+176 °F) Minimum requirement: cable temperature range ≥ ambient temperature +20 K Power supply cable				
Cable specification	 NPT ½" G ½" M20 Permitted temperature range -40 °C (-40 °F) to +80 °C (+176 °F) Minimum requirement: cable temperature range ≥ ambient temperature +20 K Power supply cable Standard installation cable is sufficient.				
Cable specification	 NPT ½" G ½" M20 Permitted temperature range -40 °C (-40 °F) to +80 °C (+176 °F) Minimum requirement: cable temperature range ≥ ambient temperature +20 K Power supply cable Standard installation cable is sufficient. Signal cable				
Cable specification	 NPT ½" G ½" M20 Permitted temperature range -40 °C (-40 °F) to +80 °C (+176 °F) Minimum requirement: cable temperature range ≥ ambient temperature +20 K Power supply cable Standard installation cable is sufficient. Signal cable Current output 				

PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz
Cable capacitance	<30 pF/m
Wire cross-section	>0.34 mm ² (22 AWG)
Cable type	Twisted pairs
Loop resistance	<110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.

Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz
Cable capacitance	<30 pF/m
Wire cross-section	>0.34 mm ² (22 AWG)
Cable type	Twisted pairs
Loop resistance	<110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.

EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.

For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization

PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.

For more information on planning and installing PROFINET networks, see: "PROFINET Cabling and Interconnection Technology", Guideline for PROFINET

Connecting cable between Safety Barrier Promass 100 and measuring device

Cable type	Shielded twisted-pair cable with 2x2 wires. When grounding the cable shield, observe the grounding concept of the plant.
Maximum cable resistance	2.5 Ω, one side



Comply with the maximum cable resistance specifications to ensure the operational reliability of the measuring device.

The maximum cable length for individual wire cross-sections is specified in the table below. Observe the maximum capacitance and inductance per unit length of the cable and connection values for hazardous areas .

Wire cros	s-section	Maximum o	able length
[mm ²]	[AWG]	[m]	[ft]
0.5	20	70	230
0.75	18	100	328
1.0	17	100	328
1.5	16	200	656
2.5	14	300	984

Performance characteristics

Reference operating conditions	 Error limits based on ISO 11631 Water with +15 to +45 °C (+59 to +113 °F) at 2 to 6 bar (29 to 87 psi) Specifications as per calibration protocol Accuracy based on accredited calibration rigs that are traced to ISO 17025. 					
	To obtain r	neasured errors, u	ise the Applicator	r sizing tool \rightarrow	76	
Maximum measured error	o.r. = of reading	; 1 g/cm ³ = 1 kg/l	; T = medium ten	nperature		
	Base accuracy					
	Design fun	damentals $\rightarrow \square 4$	4			
	Mass flow and volume flow (liquids)					
	±0.10 % o.r.					
	Mass flow (gases)					
	±0.50 % o.r. (tantalum 2.5W)					
	Density (liquids)					
		nder ating conditions	Standaro calibra	l density ation ¹⁾	Wide density spe	-range cification ^{2) 3)}
	[g/cm ³]	[lbs/in ³]	[g/cm³]	[lbs/in ³]	[g/cm³]	[lbs/in ³]
	±0.0005	±0.00097	±0.02	±0.039	±0.002	±0.0039

3) Order code for "Application package", option EF "Special density and concentration "

Temperature

 $\pm 0.5\ ^\circ C \pm 0.005 \cdot T\ ^\circ C \ (\pm 0.9\ ^\circ F \pm 0.003 \cdot (T - 32)\ ^\circ F)$

Zero point stability

D	N	Zero poin	t stability
[mm]	[in]	[kg/h]	[lb/min]
8	3⁄8	0.40	0.015
15	1/2	0.65	0.024
25	1	1.80	0.066
40	1½	9.00	0.331
50	2	14.00	0.514

Flow values

Flow values as turndown parameter depending on nominal diameter.

SI units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[mm]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]
8	2000	200	100	40	20	4
15	6500	650	325	130	65	13
25	18000	1800	900	360	180	36
40	45 000	4 500	2 2 5 0	900	450	90
50	70000	7 000	3 500	1400	700	140

US units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[inch]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]
3/8	73.50	7.350	3.675	1.470	0.735	0.147
1/2	238.9	23.89	11.95	4.778	2.389	0.478
1	661.5	66.15	33.08	13.23	6.615	1.323
11/2	1654	165.4	82.70	33.08	16.54	3.308
2	2 5 7 3	257.3	128.7	51.46	25.73	5.146

Accuracy of outputs

In the case of analog outputs, the output accuracy must also be considered for the measured error; in contrast, this need not be considered in the case of fieldbus outputs (e.g. Modbus RS485, EtherNet/IP).

The outputs have the following base accuracy specifications.

Current output


Accuracy	Max. ±5 μA
----------	------------

Pulse/frequency output

o.r. = of reading

Accuracy	Max. ± 50 ppm o.r. (across the entire ambient temperature range)
----------	--

Repeatability	o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$; T = medium temperature				
	Base repeatability				
	Mass flow and volume flow (liquids) $\pm 0.05 \%$ o.r.				
	Mass flow (gases) ±0.25 % o.r. (tantalum 2.5	5W)			
	Design fundamentals	$s \rightarrow \cong 44$			
	Density (liquids) ±0.00025 g/cm ³				
	Temperature ±0.25 ℃ ± 0.0025 · T ℃ (±	±0.45 °F ± 0.0015 · (T–32) °F)			
Response time	The response time depends on the configuration (damping).				
Influence of ambient	Current output				
temperature	o.r. = of reading				
	Temperature coefficient	Max. ±0.005% o.r./°C			
	Pulse/frequency output				
	Temperature coefficient	No additional effect. Included in accuracy.			
Influence of medium temperature	Mass flow and volume flowWhen there is a difference between the temperature for zero point adjustment and the process temperature, the typical measured error of the sensor is ± 0.0002 % of the full scale value/°C (± 0.0001 % of the full scale value/°F).DensityWhen there is a difference between the density calibration temperature and the process temperature, the typical measured error of the sensor is ± 0.0001 g/cm ³ /°C (± 0.00005 g/cm ³ /°F).Field density calibration is possible.Wide-range density specification (special density calibration) If the process temperature is outside the valid range ($\rightarrow \boxdot 41$) the measured error is ± 0.0001 g/cm ³ /°C (± 0.00005 g/cm ³ /°F)				



1 Field density calibration, for example at +20 $^{\circ}$ C (+68 $^{\circ}$ F)

2 Special density calibration

Temperature

±0.005 · T °C (± 0.005 · (T – 32) °F)

Influence of medium pressure

The table below shows the effect on accuracy of mass flow due to a difference between calibration pressure and process pressure.

o.r. = of reading

D	N	Promass H zirconium	702/R 60702	Promass H tantalum 2.5W		
[mm]	[in]	[% o.r./bar]	[% o.r./psi]	[% o.r./bar]	[% o.r./psi]	
8	3/8	-0.017	-0.0012	-0.007	-0.0005	
15	1/2	-0.021	-0.0014	-0.005	-0.0003	
25	1	-0.013	-0.0009	-0.015	-0.0010	
40	1½	-0.018	-0.0012	-0.012	-0.0008	
50	2	-0.015	-0.0010	-0.011	-0.0008	

Design fundamentals

o.r. = of reading, o.f.s. = of full scale value

BaseAccu = base accuracy in % o.r., BaseRepeat = base repeatability in % o.r.

MeasValue = measured value; ZeroPoint = zero point stability


Calculation of the maximum measured error as a function of the flow rate

Flow rate		Maximum measured error in % o.r.
$\geq \frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$		± BaseAccu
	A0021332	
$< rac{ ext{ZeroPoint}}{ ext{BaseAccu}} \cdot 100$		$\pm \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$
	A0021333	A0021334

Calculation of the maximum repeatability as a function of the flow rate

Flow rate		Maximum repeatability in % o.r.
$\geq \frac{\frac{1}{2} \cdot \text{ZeroPoint}}{\text{BaseRepeat}} \cdot 100$		± BaseRepeat
	A0021335	
$< \frac{\frac{1}{2} \cdot \text{ZeroPoint}}{\text{BaseRepeat}} \cdot 100$		$\pm \frac{1}{2} \cdot \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$
	A0021336	A0021337

Example for max. measured error




E Error: Maximum measured error as % o.r. (example)

Q Flow rate as %

Installation

No special measures such as supports are necessary. External forces are absorbed by the construction of the device.




To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

Installation in down pipes

However, the following installation suggestion allows for installation in an open vertical pipeline. Pipe restrictions or the use of an orifice with a smaller cross-section than the nominal diameter prevent the sensor running empty while measurement is in progress.



■ 19 Installation in a down pipe (e.g. for batching applications)

1 Supply tank

2 Sensor

3 Orifice plate, pipe restriction

4 Valve

5 Batching tank

D	N	Ø orifice plate, pipe restriction			
[mm]	[in]	[mm]	[in]		
8	3⁄8	6	0.24		
15	1/2	10	0.40		
25	1	14	0.55		
40	1½	22	0.87		
50	2	28	1.10		

Orientation


The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

	Orientatio	n	Recommendation
A	Vertical orientation	A0015591	
В	Horizontal orientation, transmitter head up	A0015589	I) Exceptions: → I 20, □ 47
С	Horizontal orientation, transmitter head down	A0015590	Exceptions: $\rightarrow \square 20, \square 47$
D	Horizontal orientation, transmitter head at side	A0015592	

1) Applications with low process temperatures may decrease the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.

2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.

If a sensor is installed horizontally with a curved measuring tube, match the position of the sensor to the fluid properties.



E 21 Minimum distance between additional Safety Barrier Promass 100 or other modules. Engineering unit mm (in)

Environment

Ambient temperature range	Measuring device	Non-Ex	-40 to +60 °C (-40 to +140 °F)
		Ex na, NI version	-40 to +60 °C (-40 to +140 °F)

	Ex ia, IS version	 -40 to +60 °C (-40 to +140 °F) -50 to +60 °C (-58 to +140 °F) (order code for "Test, certificate", option JM))
Readability of the local display		-20 to +60 $^\circ\text{C}$ (-4 to +140 $^\circ\text{F})$ The readability of the display may be impaired at temperatures outside the temperature range.
Safety Barrier Promass 100		-40 to +60 °C (-40 to +140 °F)

► If operating outdoors:

Avoid direct sunlight, particularly in warm climatic regions.



Weather protection covers can be ordered from Endress+Hauser: see "Accessories" section

Temperature tables

In the following tables, the following interdependencies between the maximum medium temperature T_m for T6 to T1 and the maximum ambient temperature T_a apply when operating the device in hazardous areas.

Ex ia, $_{\rm C}{\rm CSA}_{\rm US}$ IS

SI units

Order code for "Housing"	Т _а [°С]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]
	35	50	85	120	150 ¹⁾	150 ²⁾	150 ²⁾
Option A "Compact coated alu" Option B "Compact, stainless"	50	-	85	120	150 ¹⁾	150 ²⁾	150 ²⁾
option B compact, stanness	60	-	-	120	150 ¹⁾	150 ²⁾	150 ²⁾
	35	50	85	120	150 ¹⁾	150 ²⁾	150 ²⁾
Option C "Ultra-compact, stainless"	45	-	85	120	150 ¹⁾	150 ²⁾	150 ²⁾
	50	-	-	120	150 ¹⁾	150 ²⁾	150 ²⁾

1) The following applies for specified sensors with a maximum medium temperature T_m = 205 °C: T_m = 170 °C

2) The following applies for specified sensors with a maximum medium temperature $T_m = 205$ °C: $T_m = 205$ °C

Order code for "Housing"	T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]
Option A "Compact coated alu" Option B "Compact, stainless"	95	122	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
	122	-	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
option D compact, stanness	140	-	-	248	302 ¹⁾	302 ²⁾	302 ²⁾
	95	122	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
Option C "Ultra-compact, stainless"	113	-	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
	122	-	-	248	302 ¹⁾	302 ²⁾	302 ²⁾

US units

1) The following applies for specified sensors with a maximum medium temperature $T_m = 401$ °F: $T_m = 338$ °F

2) The following applies for specified sensors with a maximum medium temperature $T_m = 401 \text{ }^\circ\text{F}$: $T_m = 401 \text{ }^\circ\text{F}$

Ex nA, $_{C}CSA$ _{US} NI

SI units

Order code for "Housing"	Т _а [°С]	T6 [85 °C]	T5 [100 °C]	T4 [135 °C]	T3 [200 °C]	T2 [300 °C]	T1 [450 °C]
Option A "Compact coated alu" Option B "Compact, stainless"	35	50	85	120	150 ¹⁾	150 ²⁾	150
	50	-	85	120	150	150	150
	60	-	-	120	150	150	150
Option C "Ultra-compact, stainless"	50	-	85	120	150	150	150
	60	-	-	120	150	150	150

1) The following applies for specified sensors with a maximum medium temperature $T_m = 205$ °C: $T_m = 170$ °C

2) The following applies for specified sensors with a maximum medium temperature $T_m = 205$ °C: $T_m = 205$ °C

US units

Order code for "Housing"	T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]
Option A "Compact coated alu" Option B "Compact, stainless"	95	122	185	248	302 ¹⁾	302 ²⁾	302
	122	-	185	248	302	302	302
option D' compact, stanness	140	-	-	248	302	302	302
Option C "Ultra-compact, stainless"	122	-	185	248	302	302	302
	140	-	-	248	302	302	302

1) The following applies for specified sensors with a maximum medium temperature $T_m = 401$ °F: $T_m = 338$ °F

2) The following applies for specified sensors with a maximum medium temperature $T_m = 401$ °F: $T_m = 401$ °F


Explosion hazards arising from gas and dust

Determining the temperature class and surface temperature with the temperature table

- In the case of gas: Determine the temperature class as a function of the ambient temperature $T_{\rm a}$ and the medium temperature $T_{\rm m}.$
- In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature T_a and the maximum medium temperature T_m.

Example

- Measured maximum ambient temperature: $T_{ma} = 47 \text{ °C}$
- Measured maximum medium temperature: $T_{mm} = 108 \text{ °C}$



22 Procedure for determining the maximum surface temperature


1. Select device (optional).

	 In the column for the maximum ambient temperature T_a select the temperature that is immediately greater than or equal to the measured maximum ambient temperature T_{ma} that is present. T_a = 50 °C. The row showing the maximum medium temperature is determined.
	3. Select the maximum medium temperature T _m of this row, which is larger or equal to the measured maximum medium temperature T _{mm} .
	→ The column with the temperature class for gas is determined: 108 °C ≤ 120°C \rightarrow T4.
	4. The maximum temperature of the temperature class determined corresponds to the maximum surface temperature for dust: T4 = 135 $^{\circ}$ C
Storage temperature	–40 to +80 °C (–40 to +176 °F), preferably at +20 °C (+68 °F) (standard version)
	–50 to +80 °C (–58 to +176 °F) (Order code for "Test, certificate", option JM)
Climate class	DIN EN 60068-2-38 (test Z/AD)
Degree of protection	 Transmitter and sensor As standard: IP66/67, type 4X enclosure With the order code for "Sensor options", option CM: IP69K can also be ordered When housing is open: IP20, type 1 enclosure Display module: IP20, type 1 enclosure
	Safety Barrier Promass 100 IP20
Vibration resistance	 Compact version Vibration, sinusoidal according to IEC 60068-2-6 2 to 8.4 Hz, 3.5 mm peak 8.4 to 2 000 Hz, 1 g peak Vibration broad-band random, according to IEC 60068-2-64 10 to 200 Hz, 0.003 g²/Hz 200 to 2 000 Hz, 0.001 g²/Hz Total: 1.54 g rms
Shock resistance	Compact version Shock, half-sine according to IEC 60068-2-27 6 ms 30 g
Shock resistance	Compact version Rough handling shocks according to IEC 60068-2-31
Interior cleaning	Cleaning in place (CIP)Sterilization in place (SIP)
	Options Oil- and grease-free version for wetted parts, without inspection certificate Order code for "Service", option HA
Electromagnetic compatibility (EMC)	 Depends on the communication protocol: HART, PROFIBUS DP, Modbus RS485, EtherNet/IP: As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) PROFINET: as per IEC/EN 61326 Complies with emission limits for industry as per EN 55011 (Class A) Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170 Volume 2, IEC 61784 The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible. For details, refer to the Declaration of Conformity.

Medium temperature range	Sensor ■ Zirconium 702/R 60702: -50 to +205 °C (-58 to +401 °F) ■ Tantalum 2.5W: -50 to +150 °C (-58 to +302 °F)
	Seals No internal seals
Density	0 to 5 000 kg/m ³ (0 to 312 lb/cf)
Pressure-temperature ratings	The following pressure-temperature ratings refer to the entire device and not just the process connection.

Process


Flange connection according to EN 1092-1 (DIN 2501)



23 With flange material 1.4301 (304); wetted parts: zirconium 702, tantalum

The material load curves for the temperature range +150 to +205 $^\circ C$ (+302 to +401 $^\circ F) apply only to the order code for "Measuring tube material", option TJ$


Flange connection according to ASME B16.5




24 With flange material 1.4301 (304); wetted parts: zirconium 702, tantalum

The material load curves for the temperature range +150 to +205 $^\circ C$ (+302 to +401 $^\circ F) apply only to the order code for "Measuring tube material", option TJ$


Flange connection according to JIS B2220



Pressure loss	To calculate the pressure loss, use the <i>Applicator</i> sizing tool $\rightarrow \square$ 76
System pressure	It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas. This is prevented by means of a sufficiently high system pressure.
	For this reason, the following mounting locations are recommended:At the lowest point in a vertical pipeDownstream from pumps (no danger of vacuum)




In the case of some fluids, it is important that the heat radiated from the sensor to the transmitter is kept to a minimum. A wide range of materials can be used for the required insulation.



a Minimum distance to insulation

t maximum Insulation thickness

The minimum distance between the transmitter housing and the insulation is 10 mm (0.39 in) so that the transmitter head remains completely exposed.



26 Maximum recommended insulation thickness depending on the temperature of the medium and the ambient temperature

t	Insulation thickness
T _m	Medium temperature
T ₄₀₍₁₀₄₎	Maximum recommended insulation thickness at an ambient temperature of T_a = 40 $^\circ C$ (104 $^\circ F)$
T ₆₀₍₁₄₀₎	Maximum recommended insulation thickness at an ambient temperature of T_a = 60 °C (140 °F)

A0015594

NOTICE

Danger of overheating with insulation

► Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F)

NOTICE

The insulation can also be thicker than the maximum recommended insulation thickness. Prerequisite:

- Ensure that convection takes place on a sufficiently large scale at the transmitter neck.
- Ensure that a sufficiently large area of the housing support remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Some fluids require suitable measures to avoid loss of heat at the sensor.

Heating options

- Electrical heating, e.g. with electric band heaters
- Via pipes carrying hot water or steam
- Via heating jackets

Heating jackets for the sensors can be ordered as accessories from Endress+Hauser $\rightarrow \square$ 75.

NOTICE

Danger of overheating when heating

- ► Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F).
- Ensure that convection takes place on a sufficiently large scale at the transmitter neck.
- Ensure that a sufficiently large area of the housing support remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Vibrations

Heating


The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by plant vibrations.

Mechanical construction

Dimensions in SI units

Compact version


Order code for "Housing", option A "Compact coated alu"




DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E ¹⁾ [mm]	F ¹⁾ [mm]	G [mm]	H [mm]	L [mm]	K [mm]
8	136	147.5	93.5	54	261	369	8.51	108	2)	92
15	136	147.5	93.5	54	261	369	12.0	108	2)	92
25	136	147.5	93.5	54	261	382	17.6	121	2)	92
40	136	147.5	93.5	54	285	458	25.5	173	2)	132
50	136	147.5	93.5	54	296	537	40.5	241	2)	167

If using a display, order code for "Display; Operation", option B: values + 28 mm Dependent on the specific process connection 1)


2)





DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E ¹⁾ [mm]	F ¹⁾ [mm]	G [mm]	H [mm]	L [mm]	K [mm]
8	133.5	136.8	78	58.8	257	365	8.51	108	2)	92
15	133.5	136.8	78	58.8	257	365	12.0	108	2)	92
25	133.5	136.8	78	58.8	257	378	17.6	121	2)	92
40	133.5	136.8	78	58.8	281	454	25.5	173	2)	132
50	133.5	136.8	78	58.8	292	533	40.5	241	2)	167

1) 2) If using a display, order code for "Display; Operation", option B: values + $14~\rm{mm}$ Dependent on the specific process connection



Order code for "Housing", option C "Ultra-compact hygienic, stainless"


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E ¹⁾ [mm]	F ¹⁾ [mm]	G [mm]	H [mm]	L [mm]	K [mm]
8	114.9	123.6	67.7	55.9	256	364	8.51	108	2)	92
15	114.9	123.6	67.7	55.9	256	364	12.0	108	2)	92
25	114.9	123.6	67.7	55.9	256	377	17.6	121	2)	92
40	114.9	123.6	67.7	55.9	280	453	25.5	173	2)	132
50	114.9	123.6	67.7	55.9	291	532	40.5	241	2)	167

If using a display, order code for "Display; Operation", option B: values + $14~\rm{mm}$ Dependent on the specific process connection 1)

2)

Flange connections

Fixed flange EN 1092-1, ASME B16.5, JIS B2220



■ 27 Engineering unit mm (in)

1.4404 (316/ Order code for	316L) "Process connect	ion", option D2 V	V			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 ¹⁾	95	65	$4 \times Ø14$	20	17.3	336
15	95	65	$4 \times Ø14$	20	17.3	440
25	115	85	$4 \times Ø14$	19.0	28.5	580
40	150	110	4 × Ø18	21.5	43.1	794
50	165	125	4 × Ø18	23.5	54.5	1071

1) DN 8 with DN 15 flanges as standard

Tuer coue joi	r "Process connee	ction", option A	AW			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 ¹⁾	90	60.3	4 × Ø15.7	12.8	15.7	336
15	90	60.3	4 × Ø15.7	12.8	15.7	440
25	110	79.4	4 × Ø15.7	15.1	26.7	580
40	125	98.4	4 × Ø15.7	17.5	40.9	794
50	150	120.7	4 × Ø19.1	23.6	52.6	1071

1) DN 8 with DN 15 flanges as standard

Jidei code joi	r "Process conne	ction", option Al	BW			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 ¹⁾	95	66.7	4 × Ø15.7	14.2	15.7	336
15	95	66.7	4 × Ø15.7	14.2	15.7	440
25	125	88.9	4 × Ø19.1	17.5	26.7	580
40	155	114.3	4 × Ø22.3	20.6	40.9	794
50	165	127.0	8 × Ø19.1	23.6	52.6	1071

1) DN 8 with DN 15 flanges as standard

Flange JIS B2220: 20K 1.4404 (316/316L) Order code for "Process connection", option NEW								
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]		
8 ¹⁾	95	70	4 × Ø15	14	15	336		
15	95	70	4 × Ø15	14	15	440		
25	125	90	4 × Ø19	16	25	580		


Flange JIS B22 1.4404 (316/ Order code for		tion", option NE V	N			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
40	140	105	4 × Ø19	18	40	794
50	165	120	8 × Ø19	22	50	1071

1) DN 8 with DN 15 flanges as standard

Safety Barrier Promass 100

Top-hat rail EN 60715:

- TH 35 x 7.5
- TH 35 x 15




А	В	С	D
[mm]	[mm]	[mm]	[mm]
108	114.5	99	22.5

Accessories

Purge connections / secondary containment monitoring

Order code for "Sensor options", option CH




DN	G	А	Н	L
[mm]	[in]	[mm]	[mm]	[mm]
8	½ NPT	25	82	110
15	½ NPT	25	82	204
25	½ NPT	25	82	348
40	½ NPT	45	102	526
50	½ NPT	58	119.5	763

Dimensions in US units


Compact version

Order code for "Housing", option A "Compact coated alu"



DN [in]	A [in]	B [in]	C [in]	D [in]	E ¹⁾ [in]	F ¹⁾ [in]	G [in]	H [in]	L [in]	K [in]
3⁄8	5.35	5.81	3.68	2.13	10.3	14.5	0.34	4.25	2)	3.62
1/2	5.35	5.81	3.68	2.13	10.3	14.5	0.47	4.25	2)	3.62
1	5.35	5.81	3.68	2.13	10.3	15.0	0.69	4.76	2)	3.62
1½	5.35	5.81	3.68	2.13	11.2	18.0	1	6.81	2)	5.2
2	5.35	5.81	3.68	2.13	11.7	21.1	1.59	9.49	2)	6.57


If using a display, order code for "Display; Operation", option B: values + $1.1\ in$ Dependent on the specific process connection 1) 2)



Order code for "Housing", option B "Compact hygienic, stainless"

DN [in]	A [in]	B [in]	C [in]	D [in]	E ¹⁾ [in]	F ¹⁾ [in]	G [in]	H [in]	L [in]	K [in]
3/8	5.26	5.39	3.07	2.31	10.1	14.4	0.34	4.25	2)	3.62
1/2	5.26	5.39	3.07	2.31	10.1	14.4	0.47	4.25	2)	3.62
1	5.26	5.39	3.07	2.31	10.1	14.9	0.69	4.76	2)	3.62
1½	5.26	5.39	3.07	2.31	11.1	17.9	1	6.81	2)	5.2
2	5.26	5.39	3.07	2.31	11.5	21.0	1.59	9.49	2)	6.57

If using a display, order code for "Display; Operation", option B: values + 0.55 in Dependent on the specific process connection 1) 2)



Order code for "Housing", option C "Ultra-compact hygienic, stainless"


A0019438

DN [in]	A [in]	B [in]	C [in]	D [in]	E ¹⁾ [in]	F ¹⁾ [in]	G [in]	H [in]	L [in]	K [in]
3⁄8	4.39	4.87	2.67	2.2	10.1	14.3	0.34	4.25	2)	3.62
1/2	4.39	4.87	2.67	2.2	10.1	14.3	0.47	4.25	2)	3.62
1	4.39	4.87	2.67	2.2	10.1	14.8	0.69	4.76	2)	3.62
1½	4.39	4.87	2.67	2.2	11.0	17.8	1	6.81	2)	5.2
2	4.39	4.87	2.67	2.2	11.5	20.9	1.59	9.49	2)	6.57

If using a display, order code for "Display; Operation", option B: values + 0.55 in Dependent on the specific process connection 1) 2)

Flange connections

Fixed flange ASME B16.5



🖸 28 Engineering unit mm (in)

Order code _.	for "Process cor	nection", optio	n AAW			
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
3/8 1)	3.54	2.37	4 × Ø0.62	0.50	0.62	13.23
1/2	3.54	2.37	4 × Ø0.62	0.50	0.62	17.32
1	4.33	3.13	4 × Ø0.62	0.59	1.05	22.83
11/2	4.92	3.87	4 × Ø0.62	0.69	1.61	31.26
2	5.91	4.75	4 × Ø0.75	0.93	2.07	42.17

Surface roughness (flange): Ra 125 to 248 µin

1) DN $\frac{3}{8}$ " with DN $\frac{1}{2}$ " flanges as standard


1.4404 (31	ording to ASM 6/316L) for "Process cor					
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
3/8 1)	3.74	2.63	4 × Ø0.62	0.56	0.62	13.23
1/2	3.74	2.63	4 × Ø0.62	0.56	0.62	17.32
1	4.92	3.50	4 × Ø0.75	0.69	1.05	22.83
1½	6.10	4.50	4 × Ø0.88	0.81	1.61	31.26
2	6.50	5.00	8 × Ø0.75	0.93	2.07	42.17
		Surface	roughness (flange): Ra 12	5 to 248 µin		

1) DN $^{3}\!/_{\!8}"$ with DN $^{4}\!/_{\!2}"$ flanges as standard

Safety Barrier Promass 100

Top-hat rail EN 60715:

- TH 35 x 7.5
- TH 35 x 15




А	В	С	D
[in]	[in]	[in]	[in]
4.25	4.51	3.9	0.89

Accessories

Purge connections / secondary containment monitoring

Order code for "Sensor options", option CH



DN	G	А	Н	L
[in]	[in]	[in]	[in]	[in]
3⁄8	½ NPT	0.98	3.23	4.34
1/2	½ NPT	0.98	3.23	8.04
1	½ NPT	0.98	3.23	13.54
11/2	½ NPT	1.77	4.02	20.70
2	½ NPT	2.28	4.70	30.04

Weight

Compact version

Weight in SI units

All values (weight) refer to devices with EN/DIN PN 40 flanges. Weight information in [kg].

DN [mm]	Weight [kg]
8	10
15	11
25	17
40	34
50	67

Weight in US units

All values (weight) refer to devices with EN/DIN PN 40 flanges. Weight information in [lbs].

DN [in]	Weight [lbs]
3/8	22
1/2	24
1	37
11/2	75
2	148

Safety Barrier Promass 100


49 g (1.73 ounce)

Materials

Transmitter housing

- Order code for "Housing", option A "Compact, aluminum coated": Aluminum, AlSi10Mq, coated
- Order code for "Housing", option B "Compact, stainless": Stainless steel 1.4301 (304)
- Order code for "Housing", option C "Ultra-compact, stainless": Stainless steel 1.4301 (304)
- Window material for optional local display ($\rightarrow \implies 67$):
 - For order code for "Housing", option $\hat{\mathbf{A}}$: glass
 - For order code for "Housing", option **B** and **C**: plastic

Cable entries/cable glands



29 Possible cable entries/cable glands

1 Cable entry in transmitter housing with internal thread M20 x 1.5

2 Cable gland M20 x 1.5

3 Adapter for cable entry with internal thread G $\frac{1}{2}$ or NPT $\frac{1}{2}$

Order code for "Housing", option A "Compact, coated aluminum"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Nickel-plated brass
Adapter for cable entry with internal thread G $\frac{1}{2}$ "	
Adapter for cable entry with internal thread NPT $\frac{1}{2}$ "	

Order code for "Housing", option B "Compact, stainless"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Stainless steel, 1.4404 (316L)
Adapter for cable entry with internal thread G $\frac{1}{2}$ "	
Adapter for cable entry with internal thread NPT $\frac{1}{2}$ "	

Device plug

Electrical connection	Material
Plug M12x1	 Socket: Stainless steel, 1.4404 (316L) Contact housing: Polyamide Contacts: Gold-plated brass

Sensor housing

- Acid and alkali-resistant outer surface
- Stainless steel 1.4301 (304)

Measuring tubes

- Zirconium 702/R 60702Tantalum 2.5W

Process connections

- Stainless steel, 1.4301 (304); wetted parts: zirconium 702, tantalum
- Flanges according to EN 1092-1 (DIN 2501) / according to ASME B16.5 / according to JIS B2220
 - H

Seals

Welded process connections without internal seals

Safety Barrier Promass 100

Housing: Polyamide

Process connections	Fixed flange connections: – EN 1092-1 (DIN 2501) flange – EN 1092-1 (DIN 2512N) flange – ASME B16.5 flange – JIS B2220 flange	
	For information on the different materials used in the process connections $\rightarrow \square$ 65	
Surface roughness	All data relate to parts in contact with fluid. Not polished	

Operability

Operating concept	Operator-oriented menu structure for user-specific tasks Commissioning Operation Diagnostics Expert level
	 Quick and safe commissioning Individual menus for applications Menu guidance with brief explanations of the individual parameter functions
	 Reliable operation Operation in the following languages: Via "FieldCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese Via integrated Web browser (only available for device versions with HART, PROFIBUS DP, PROFINET and EtherNet/IP): English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech, Swedish, Korean Uniform operating philosophy applied to operating tools and Web browser If replacing the electronic module, transfer the device configuration via the plug-in memory (HistoROM DAT) which contains the process and measuring device data and the event logbook. No need to reconfigure. For devices with Modbus RS485, the data recovery function is implemented without the plug-in memory (HistoROM DAT).

Efficient diagnostics increase measurement availability	Efficient diagnostics	increase measurement	t availability
---	------------------------------	----------------------	----------------

- Troubleshooting measures can be called up via the operating tools and Web browser
- Diverse simulation options
- Status indicated by several light emitting diodes (LEDs) on the electronic module in the housing compartment

Local display

A local display is only available for device versions with the following communication protocols: HART, PROFIBUS-DP, PROFINET, EtherNet/IP

The local display is only available with the following device order code: Order code for "Display; Operation", option **B**: 4-line; lit, via communication

Display element


1

- 4-line liquid crystal display with 16 characters per line.
- White background lighting; switches to red in event of device errors.
- Format for displaying measured variables and status variables can be individually configured.
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F). The readability of the display may be impaired at temperatures outside the temperature range.

Remote operation

Via HART protocol

This communication interface is available in device versions with a HART output.




30 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 VIATOR Bluetooth modem with connecting cable
- 7 Transmitter

Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




■ 31 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Measuring device

Via Ethernet-based fieldbus

This communication interface is available in device versions with EtherNet/IP.




32 Options for remote operation via Ethernet-based fieldbus

- 1 Control system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Add-on Profile Level 3 for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 4 Ethernet switch
- 5 Measuring device

Via PROFINET network

This communication interface is available in device versions with PROFINET.



🛃 33 Options for remote operation via PROFINET network

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Switch, e.g. Scalance X204 (Siemens)
- Measuring device 4


Service interface

Via service interface (CDI-RJ45)

This communication interface is present in the following device version:

- Order code for "Output", option **B**: 4-20 mA HART, pulse/frequency/switch output
- Order code for "Output", option L: PROFIBUS DP
 Order code for "Output", option N: EtherNet/IP
- Order code for "Output", option R: PROFINET


HART



🛃 34 Connection for the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output

- Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server 1
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


PROFIBUS DP



☑ 35 Connection for order code for "Output", option L: PROFIBUS DP

- 1 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


EtherNet/IP



36 Connection for order code for "Output", option N: EtherNet/IP

- 1 Service interface (CDI -RJ45) and EtherNet/IP interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

PROFINET




■ 37 Connection for order code for "Output", option R: PROFINET

- 1 Service interface (CDI -RJ45) and PROFINET interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

Via service interface (CDI)

This communication interface is present in the following device version: Order code for "Output", option **M**: Modbus RS485

Modbus RS485



- 1 Service interface (CDI) of the measuring device
- 2 Commubox FXA291
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

Certificates and approvals

CE mark	The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied.
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
C-Tick symbol	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.

ATEX/IECEx

Currently, the following versions for use in hazardous areas are available:

Ex ia

Category (ATEX)	Type of protection
II2G	Ex ia IIC T6T1 Gb
II2G	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb
II1/2G, II2D	Ex ia IIC T6T1 Ga/Gb or Ex ia IIB T6T1 Ga/Gb Ex tb IIIC Txx °C Db
II2G, II2D	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb Ex tb IIIC Txx °C Db

Ex nA

Category (ATEX)	Type of protection
II3G	Ex nA IIC T6T1 Gc or Ex nA IIC T5-T1 Gc

$_{\rm C}{\rm CSA}_{\rm US}$

Currently, the following versions for use in hazardous areas are available:

IS (Ex i)

 Class I Division 1 Groups ABCD • Class II Division 1 Groups EFG and Class III NI (Ex nA) Class I Division 2 Groups ABCD

HART certification	HART interface	
	 The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications: Certified according to HART 7 The device can also be operated with certified devices of other manufacturers (interoperability) 	
Certification PROFIBUS	PROFIBUS interface	
	 The measuring device is certified and registered by the PROFIBUS User Organization (PNO). The measuring system meets all the requirements of the following specifications: Certified in accordance with PROFIBUS PA Profile 3.02 The device can also be operated with certified devices of other manufacturers (interoperability) 	
Certification PROFINET	PROFINET interface	
	 The measuring device is certified and registered by the PNO (PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications: Certified according to: Test specification for PROFINET devices PROFINET Security Level 1 – Net load test The device can also be operated with certified devices of other manufacturers (interoperability) 	

EtherNet/IP certification	 The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications: Certified in accordance with the ODVA Conformance Test EtherNet/IP Performance Test EtherNet/IP PlugFest compliance The device can also be operated with certified devices of other manufacturers (interoperability)
Modbus RS485 certification	The measuring device meets all the requirements of the MODBUS/TCP conformity test and has the "MODBUS/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out and is certified by the "MODBUS/TCP Conformance Test Laboratory" of the University of Michigan.
Pressure Equipment Directive	The devices can be ordered with or without a PED approval. If a device with a PED approval is required, this must be explicitly stated in the order. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary.
	 With the PED/G1/x (x = category) marking on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements" specified in Annex I of the Pressure Equipment Directive 97/23/EC. Devices bearing this marking (PED) are suitable for the following types of medium: Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to0.5 bar (7.3 psi) Unstable gases Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Art.3 Section 3 of the Pressure Equipment Directive 97/23/EC. The range of application is indicated in tables 6 to 9 in Annex II of the Pressure Equipment Directive.
Other standards and guidelines	 EN 60529 Degrees of protection provided by enclosures (IP code) IEC/EN 60068-2-6 Environmental influences: Test procedure - Test Fc: vibrate (sinusoidal). IEC/EN 60068-2-31 Environmental influences: Test procedure - Test Ec: shocks due to rough handling, primarily for devices. EN 61010-1 Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements IEC/EN 61326 Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements). NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment NAMUR NE 32 Data retention in the event of a power failure in field and control instruments with microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital transmitters with analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronics NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications NAMUR NE 132 Coriolis mass meter

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select your country → Products → Select measuring technology, software or components → Select the product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product opens.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
 - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
 - Automatic verification of exclusion criteria
 - Automatic creation of the order code and its breakdown in PDF or Excel output format
 - Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Detailed information on the application packages:

- Special Documentation for the device
- Special Documentation for the device

Heartbeat Technology	Package	Description
	Heartbeat Verification +Monitoring	 Heartbeat Monitoring Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to: Draw conclusions - using these data and other information - about the impact process influences (such as corrosion, abrasion, buildup etc.) have on the measuring performance over time. Schedule servicing in time. Monitor the process or product quality, e.g. gas pockets.
		 Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". Functional testing in the installed state without interrupting the process. Traceable verification results on request, including a report. Simple testing process via local operation or other operating interfaces. Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. Extension of calibration intervals according to operator's risk assessment.

Concentration

Package	Description
Concentration measurement and special density	Calculation and outputting of fluid concentrations Many applications use density as a key measured value for monitoring quality or controlling processes. The device measures the density of the fluid as standard and makes this value available to the control system. The "Special Density" application package offers high-precision density measurement over a wide density and temperature range particularly for applications subject to varying process conditions.
	 With the help of the "Concentration Measurement" application package, the measured density is used to calculate other process parameters: Temperature-compensated density (reference density). Percentage mass of the individual substances in a two-phase fluid. (Concentration in %). Fluid concentration is output with special units (°Brix, °Baumé, °API, etc.) for standard applications.
	The measured values are output via the digital and analog outputs of the device.

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories For the sensor

Accessories	Description
Heating jacket	Is used to stabilize the temperature of the fluids in the sensor. Water, water vapor and other non-corrosive liquids are permitted for use as fluids. If using oil as a heating medium, please consult with Endress+Hauser. For details, see Operating Instructions BA00099D

Communication-specific accessories	Accessories	Description
	Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. For details, see the "Technical Information" document TI405C/07
	HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. For details, see "Technical Information" TI00429F and Operating Instructions BA00371F
	Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. For details, see Operating Instructions BA00061S
	Fieldgate FXA320	Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00053S

Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser.	
	For details, see "Technical Information" TI00025S and Operating Instructions BA00051S	
Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area .	
	For details, see Operating Instructions BA01202S	
Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area and the Ex area .	
	For details, see Operating Instructions BA01202S	

Service-specific accessories	Accessories	Description
	Applicator	 Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections. Graphic illustration of the calculation results
		Administration, documentation and access to all project-related data and parameters throughout the entire life cycle of a project.
		Applicator is available:Via the Internet: https://wapps.endress.com/applicatorOn CD-ROM for local PC installation.
	W@M	Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records. W@M is available:
		 Via the Internet: www.endress.com/lifecyclemanagement On CD-ROM for local PC installation.
	FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.
		For details, see Operating Instructions BA00027S and BA00059S
	DeviceCare	Tool for connecting and configuring Endress+Hauser field devices.
		For details, see Innovation brochure IN01047S
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop.
		For details, see "Technical Information" TI00405C

System components

Accessories	Description
Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.
	For details, see "Technical Information" TI00133R and Operating Instructions BA00247R
iTEMP	The temperature transmitters can be used in all applications and are suitable for the measurement of gases, steam and liquids. They can be used to read in the fluid temperature.
	For details, see "Fields of Activity", FA00006T

Supplementary documentation

For an overview of the scope of the associated Technical Documentation, refer to the following: The *W@M Device Viewer* : Enter the serial number from the nameplate

- (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation

Brief Operating Instructions

Brief Operating Instructions containing the most important information for standard commissioning are supplied with the device.

Operating Instructions

	Documentation code				
Measuring device	HART	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET
Promass H 100	BA01189D	BA01250D	BA01177D	BA01184D	BA01428D

Description of device parameters

	Documentation code				
Measuring device	HART	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET
Promass 100	GP01033D	GP01034D	GP01035D	GP01036D	GP01037D

Supplementary device-

Safety Instructions

dependent documentation

Content	Documentation code
ATEX/IECEx Ex i	XA00159D
ATEX/IECEx Ex nA	XA01029D
cCSAus IS	XA00160D
INMETRO Ex i	XA01219D
INMETRO Ex nA	XA01220D
NEPSI Ex i	XA01249D
NEPSI Ex nA	XA01262D

Special Documentation

Content	Documentation code
Information on the Pressure Equipment Directive	SD00142D
Modbus RS485 Register Information	SD00154D
Concentration Measurement	SD01152D
Heartbeat Technology	SD01153D

Installation Instructions

Contents	Documentation code
Installation Instructions for spare part sets	Specified for each individual accessory

Registered trademarks

HART®

Registered trademark of the HART Communication Foundation, Austin, USA

PROFIBUS®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

EtherNet/IPTM

Trademark of ODVA, Inc.

PROFINET®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

Microsoft®

Registered trademark of the Microsoft Corporation, Redmond, Washington, USA

TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA

Applicator[®], FieldCare[®], DeviceCare[®], Field XpertTM, HistoROM[®], TMB[®], Heartbeat TechnologyTM

Registered or registration-pending trademarks of the Endress+Hauser Group

www.addresses.endress.com

