

# Technical Information

## Micropilot FMR63B

### HART

Free space radar



## Level measurement in hygienic applications

### Application

- Continuous, non-contact level measurement of liquids in hygienic applications
- Process connections: For hygiene applications (e.g.: Tri-Clamp or M24 adapter concept)
- Maximum measuring range: 80 m (262 ft)
- Temperature: -40 to +200 °C (-40 to +392 °F)
- Pressure: -1 to +25 bar (-14.5 to +363 psi)
- Accuracy: ±1 mm (±0.04 in)

### Your benefits

- PTFE or PEEK antenna for hygienic requirements
- Reliable measurement thanks to strong signal focusing, even with multiple internal fixtures
- Easy, guided commissioning with intuitive user interface
- *Bluetooth*® wireless technology for commissioning, operation and maintenance
- SIL2 as per IEC 61508, SIL3 for homogeneous redundancy
- Longer calibration cycles with Radar Accuracy Index

## Table of contents

<b>Important document information</b> . . . . .	<b>4</b>	<b>Process</b> . . . . .	<b>39</b>
Symbols . . . . .	4	Process pressure range . . . . .	39
Graphic conventions . . . . .	5	Dielectric constant . . . . .	41
<b>Function and system design</b> . . . . .	<b>5</b>	<b>Mechanical construction</b> . . . . .	<b>41</b>
Measuring principle . . . . .	5	Dimensions . . . . .	41
<b>Input</b> . . . . .	<b>6</b>	Weight . . . . .	51
Measured variable . . . . .	6	Materials . . . . .	52
Measuring range . . . . .	6	<b>Operability</b> . . . . .	<b>55</b>
Operating frequency . . . . .	13	Operating concept . . . . .	55
Transmission power . . . . .	13	Languages . . . . .	55
<b>Output</b> . . . . .	<b>13</b>	Local operation . . . . .	56
Output signal . . . . .	13	Local display . . . . .	56
Signal on alarm . . . . .	14	Remote operation . . . . .	57
Linearization . . . . .	14	System integration . . . . .	57
Load . . . . .	14	Supported operating tools . . . . .	57
Protocol-specific data . . . . .	15	<b>Certificates and approvals</b> . . . . .	<b>57</b>
Wireless HART data . . . . .	15	CE mark . . . . .	57
<b>Power supply</b> . . . . .	<b>16</b>	RoHS . . . . .	57
Terminal assignment . . . . .	16	RCM marking . . . . .	57
Terminals . . . . .	17	Ex approvals . . . . .	57
Available device plugs . . . . .	17	Functional safety . . . . .	58
Supply voltage . . . . .	18	Pressure equipment with permitted pressure ≤ 200 bar (2 900 psi) . . . . .	58
Potential equalization . . . . .	18	Radio approval . . . . .	58
Cable entries . . . . .	19	EN 302372 radio standard . . . . .	58
Cable specification . . . . .	19	FCC . . . . .	58
Overvoltage protection . . . . .	20	Industry Canada . . . . .	58
<b>Performance characteristics</b> . . . . .	<b>20</b>	Other standards and guidelines . . . . .	59
Reference operating conditions . . . . .	20	<b>Ordering information</b> . . . . .	<b>59</b>
Maximum measured error . . . . .	20	Calibration . . . . .	59
Measured value resolution . . . . .	21	Service . . . . .	60
Response time . . . . .	21	Test, certificate, declaration . . . . .	60
Influence of ambient temperature . . . . .	21	Identification . . . . .	60
Influence of gas phase . . . . .	21	<b>Application packages</b> . . . . .	<b>61</b>
<b>Mounting</b> . . . . .	<b>22</b>	Heartbeat Technology . . . . .	61
Mounting location . . . . .	22	<b>Accessories</b> . . . . .	<b>62</b>
Orientation . . . . .	23	Weather protection cover 316L . . . . .	62
Installation instructions . . . . .	24	Plastic weather protection cover . . . . .	62
Beam angle . . . . .	25	M12 socket . . . . .	63
Special mounting instructions . . . . .	26	Remote display FHX50B . . . . .	64
<b>Environment</b> . . . . .	<b>28</b>	Gas-tight feedthrough . . . . .	65
Ambient temperature range . . . . .	28	Process adapter M24 . . . . .	65
Ambient temperature limits . . . . .	28	Commubox FXA195 HART . . . . .	65
Storage temperature . . . . .	38	HART Loop Converter HMX50 . . . . .	65
Climate class . . . . .	38	FieldPort SWA50 . . . . .	65
Installation height as per IEC61010-1 Ed.3 . . . . .	38	Wireless HART adapter SWA70 . . . . .	65
Degree of protection . . . . .	38	Fieldgate FXA42 . . . . .	65
Vibration resistance . . . . .	39	Field Xpert SMT70 . . . . .	66
Electromagnetic compatibility (EMC) . . . . .	39	DeviceCare SFE100 . . . . .	66
		FieldCare SFE500 . . . . .	66
		Memograph M . . . . .	66

RN42 ..... 66

**Documentation ..... 66**

Document function ..... 66

**Registered trademarks ..... 67**

## Important document information

### Symbols

#### Safety symbols



This symbol alerts you to a dangerous situation. Failure to avoid this situation will result in serious or fatal injury.



This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in serious or fatal injury.



This symbol alerts you to a dangerous situation. Failure to avoid this situation can result in minor or medium injury.



This symbol contains information on procedures and other facts which do not result in personal injury.

#### Electrical symbols



Direct current



Alternating current



Direct current and alternating current



#### Ground connection

A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.



#### Protective earth (PE)

Ground terminals that must be connected to ground prior to establishing any other connections. The ground terminals are located on the inside and outside of the device.

- Inner ground terminal; protective earth is connected to the mains supply.
- Outer ground terminal; device is connected to the plant grounding system.

#### Symbols for certain types of information and graphics



#### Permitted

Procedures, processes or actions that are permitted



#### Preferred

Procedures, processes or actions that are preferred



#### Forbidden

Procedures, processes or actions that are forbidden



#### Tip

Indicates additional information



Reference to documentation



Reference to graphic

1, 2, 3, ...

Item numbers

A, B, C, ...

Views



#### Hazardous area

Indicates the hazardous area



#### Safe area (non-hazardous area)

Indicates the non-hazardous area


**Graphic conventions**

- Installation, explosion and electrical connection drawings are presented in simplified format
- Devices, assemblies, components and dimensional drawings are presented in reduced-line format
- Dimensional drawings are not to-scale representations; the dimensions indicated are rounded off to 2 decimal places
- Unless otherwise described, flanges are presented with sealing surface form EN1091-1, B2; ASME B16.5, RF; JIS B2220, RF

## Function and system design

**Measuring principle**

The Micropilot is a "downward-looking" measuring system, operating based on the frequency modulated continuous wave method (FMCW). The antenna emits an electromagnetic wave at a continuously varying frequency. This wave is reflected by the product and received again by the antenna.




A0032017

**1** FMCW principle: transmission and reflection of the continuous wave

*R* Reference point of measurement

*D* Distance between reference point and product surface

The frequency of this wave is modulated in the form of a sawtooth signal between two limit frequencies  $f_1$  and  $f_2$ :



A0023771

**2** FMCW principle: result of frequency modulation

*1* Transmitted signal

*2* Received signal

This results in the following difference frequency at any time between the transmitted signal and the received signal:

$$\Delta f = k \Delta t$$

where  $\Delta t$  is the run time and  $k$  is the specified increase in frequency modulation.

$\Delta t$  is given by the distance  $D$  between the reference point  $R$  and the product surface:

$$D = (c \Delta t) / 2$$

where  $c$  is the speed of propagation of the wave.

In summary,  $D$  can be calculated from the measured difference frequency  $\Delta f$ .  $D$  is then used to determine the content of the tank or silo.

## Input

<b>Measured variable</b>	The measured variable is the distance between the reference point and the product surface. The level is calculated based on "E", the empty distance entered.
--------------------------	--

<b>Measuring range</b>	The measuring range starts at the point where the beam hits the tank floor. Levels below this point cannot be measured, particularly in the case of spherical bases or conical outlets.
------------------------	---

### Maximum measuring range

The maximum measuring range depends on the antenna size and design.


Antenna	Maximum measuring range
Integrated, PEEK, 20 mm (0.75 in)	10 m (32.8 ft)
Cladded flush mount, PTFE, 50 mm (2 in)	50 m (164 ft)
Cladded flush mount, PTFE, 80 mm (3 in)	80 m (262 ft)

### Usable measuring range

The usable measuring range depends on the antenna size, the medium's reflective properties, the installation position and any possible interference reflections.

In principle, measurement is possible up to the tip of the antenna.

To avoid any material damage from corrosive or aggressive media or deposit buildup on the antenna, the end of the measuring range should be selected 10 mm (0.4 in) before the tip of the antenna.



A0051658

### 3 Usable measuring range

- A Length of antenna + 10 mm (0.4 in)
- B Usable measuring range
- C 50 to 80 mm (1.97 to 3.15 in); medium  $\epsilon_r < 2$
- H Vessel height
- R Reference point of measurement, varies depending on the antenna system

For further information on the reference point, see → Mechanical construction.

In the case of media with a low dielectric constant,  $\epsilon_r < 2$ , the tank floor may be visible through the medium at very low levels (lower than level C). Reduced accuracy must be expected in this range. If this is not acceptable, the zero point should be positioned at a distance C above the tank floor in these applications → Usable measuring range.

The media groups and the possible measuring range are described as a function of the application and media group in the following section. If the dielectric constant of the medium is not known, to ensure a reliable measurement assume the medium belongs to group B.

**Media groups**

- **A0** ( $\epsilon_r$  1.2 to 1.4)  
e.g. n-butane, liquid nitrogen, liquid hydrogen
- **A** ( $\epsilon_r$  1.4 to 1.9)  
Non-conductive liquids, e.g. liquefied gas
- **B** ( $\epsilon_r$  1.9 to 4)  
Non-conductive liquids, e.g. gasoline, oil, toluene, etc.
- **C** ( $\epsilon_r$  4 to 10)  
e.g. concentrated acid, organic solvents, ester, aniline, etc.
- **D** ( $\epsilon_r > 10$ )  
Conductive liquids, aqueous solutions, diluted acids, bases and alcohol

**i Measurement of the following media with absorbing gas phase**

For example:

- Ammonia
- Acetone
- Methylene chloride
- Methyl ethyl ketone
- Propylene oxide
- VCM (vinyl chloride monomer)

To measure absorbing gases, either use a guided radar, measuring devices with another measuring frequency or another measuring principle.

If measurements must be performed in one of these media, please contact Endress+Hauser.


**i For the dielectric constants (DC values) of many media commonly used in industry, please refer to:**

- Dielectric constant (DC value) Compendium CP01076F
- The Endress+Hauser "DC Values app" (available for Android and iOS)

*Measurement in storage vessel***Storage vessel - measuring conditions**


Calm medium surface (e.g. bottom filling, filling via immersion tube or rare filling from above)

*Integrated antenna, PEEK, 20 mm (0.75 in) in storage vessel*


	Media group	Measuring range
	<b>A0</b> ( $\epsilon_r$ 1.2 to 1.4)	1.5 m (5 ft)
	<b>A</b> ( $\epsilon_r$ 1.4 to 1.9)	2.5 m (8 ft)
	<b>B</b> ( $\epsilon_r$ 1.9 to 4)	5 m (16 ft)
	<b>C</b> ( $\epsilon_r$ 4 to 10)	8 m (26 ft)
	<b>D</b> ( $\epsilon_r > 10$ )	10 m (33 ft)




*Antenna, PTFE cladded flush mount, 50 mm (2 in) in storage vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	7 m (23 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	12 m (39 ft)
	B ( $\epsilon_r$ 1.9 to 4)	23 m (75 ft)
	C ( $\epsilon_r$ 4 to 10)	40 m (131 ft)
	D ( $\epsilon_r$ >10)	50 m (164 ft)


*Antenna, PTFE cladded flush mount, 80 mm (3 in) in storage vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	22 m (72 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	40 m (131 ft)
	B ( $\epsilon_r$ 1.9 to 4)	50 m (164 ft)
	C ( $\epsilon_r$ 4 to 10)	65 m (231 ft)
	D ( $\epsilon_r$ >10)	80 m (262 ft)

*Cladde antenna, PEEK, 20 mm (0.75 in) in storage vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	1.5 m (5 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	2.5 m (8 ft)
	B ( $\epsilon_r$ 1.9 to 4)	5 m (16 ft)
	C ( $\epsilon_r$ 4 to 10)	8 m (26 ft)
	D ( $\epsilon_r$ >10)	10 m (33 ft)


*Cladded antenna, PEEK, 40 mm (1.5 in) in storage vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	3 m (10 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	6 m (20 ft)
	B ( $\epsilon_r$ 1.9 to 4)	11 m (36 ft)
	C ( $\epsilon_r$ 4 to 10)	15 m (49 ft)
	D ( $\epsilon_r$ >10)	22 m (72 ft)


*Measurement in buffer vessel***Buffer vessel - measuring conditions**

Moving medium surface (e.g. permanent free filling from above, mixing jets)


*Integrated antenna, PEEK, 20 mm (0.75 in) in buffer vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	1 m (3.3 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	1.5 m (5 ft)
	B ( $\epsilon_r$ 1.9 to 4)	3 m (10 ft)
	C ( $\epsilon_r$ 4 to 10)	6 m (20 ft)
	D ( $\epsilon_r$ >10)	8 m (26 ft)


*Antenna, PTFE cladded flush mount, 50 mm (2 in) in buffer vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	4 m (13 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	7 m (23 ft)
	B ( $\epsilon_r$ 1.9 to 4)	13 m (43 ft)
	C ( $\epsilon_r$ 4 to 10)	28 m (92 ft)
	D ( $\epsilon_r$ >10)	44 m (144 ft)


*Antenna, PTFE clad flush mount, 80 mm (3 in) in buffer vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	12 m (39 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	23 m (75 ft)
	B ( $\epsilon_r$ 1.9 to 4)	45 m (148 ft)
	C ( $\epsilon_r$ 4 to 10)	60 m (197 ft)
	D ( $\epsilon_r$ >10)	70 m (230 ft)

*Cladded antenna, PEEK, 20 mm (0.75 in) in buffer vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	1 m (3.3 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	1.5 m (5 ft)
	B ( $\epsilon_r$ 1.9 to 4)	3 m (10 ft)
	C ( $\epsilon_r$ 4 to 10)	6 m (20 ft)
	D ( $\epsilon_r$ >10)	8 m (26 ft)


*Cladded antenna, PEEK, 40 mm (1.5 in) in buffer vessel*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	1.5 m (5 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	3 m (10 ft)
	B ( $\epsilon_r$ 1.9 to 4)	6 m (20 ft)
	C ( $\epsilon_r$ 4 to 10)	13 m (43 ft)
	D ( $\epsilon_r$ >10)	20 m (66 ft)


*Measurement in vessel with agitator***Vessel with agitator - measuring conditions**

Turbulent medium surface (e.g. from filling from above, stirrers and baffles)


*Integrated antenna, PEEK, 20 mm (0.75 in) in vessel with agitator*

	Media group	Measuring range
	A ( $\epsilon_r$ 1.4 to 1.9)	1 m (3.3 ft)
	B ( $\epsilon_r$ 1.9 to 4)	1.5 m (5 ft)
	C ( $\epsilon_r$ 4 to 10)	3 m (10 ft)
	D ( $\epsilon_r > 10$ )	5 m (16 ft)


*Antenna, PTFE clad flush mount, 50 mm (2 in) in vessel with agitator*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	2 m (7 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	4 m (13 ft)
	B ( $\epsilon_r$ 1.9 to 4)	7 m (23 ft)
	C ( $\epsilon_r$ 4 to 10)	15 m (49 ft)
	D ( $\epsilon_r > 10$ )	25 m (82 ft)


*Antenna, PTFE clad flush mount, 80 mm (3 in) in vessel with agitator*

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	7 m (23 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	13 m (43 ft)
	B ( $\epsilon_r$ 1.9 to 4)	25 m (82 ft)
	C ( $\epsilon_r$ 4 to 10)	50 m (164 ft)
	D ( $\epsilon_r > 10$ )	60 m (197 ft)

Cladded antenna, PEEK, 20 mm (0.75 in) in vessel with agitator

	Media group	Measuring range
	A ( $\epsilon_r$ 1.4 to 1.9)	1 m (3.3 ft)
	B ( $\epsilon_r$ 1.9 to 4)	1.5 m (5 ft)
	C ( $\epsilon_r$ 4 to 10)	3 m (10 ft)
	D ( $\epsilon_r$ >10)	5 m (16 ft)

Cladded antenna, PEEK, 40 mm (1.5 in) in vessel with agitator

	Media group	Measuring range
	A0 ( $\epsilon_r$ 1.2 to 1.4)	1 m (3.3 ft)
	A ( $\epsilon_r$ 1.4 to 1.9)	1.5 m (5 ft)
	B ( $\epsilon_r$ 1.9 to 4)	3 m (10 ft)
	C ( $\epsilon_r$ 4 to 10)	7 m (23 ft)
	D ( $\epsilon_r$ >10)	11 m (36 ft)

Operating frequency	Approx. 80 GHz
	Up to 8 devices can be installed in a tank without the devices mutually influencing one another.
Transmission power	<ul style="list-style-type: none"><li>■ Peak power: &lt;1.5 mW</li><li>■ Average output power: &lt;70 <math>\mu</math>W</li></ul>

## Output

Output signal	HART
	Signal coding: FSK $\pm$ 0.5 mA over current signal
	Data transmission rate: 1 200 Bit/s
	Galvanic isolation: Yes
	Current output 4 to 20 mA with superimposed digital communication protocol HART, 2-wire

The current output offers a choice of three different operating modes:

- 4.0 to 20.5 mA
- NAMUR NE 43: 3.8 to 20.5 mA (factory setting)
- US mode: 3.9 to 20.8 mA

## Signal on alarm

### Current output

Failure mode (according to NAMUR Recommendation NE 43):

- Minimum alarm (= factory setting): 3.6 mA
- Maximum alarm: 22 mA
- Failure mode with user-configurable value: 3.59 to 22.5 mA

### Local display

Status signal (according to NAMUR Recommendation NE 107):

Plain text display

### Operating tool via service interface (CDI)

Status signal (according to NAMUR Recommendation NE 107):

Plain text display

### Operating tool via HART communication

Status signal (according to NAMUR Recommendation NE 107):

Plain text display

## Linearization

The linearization function of the device allows the conversion of the measured value into any unit of length, weight, flow or volume.

### Pre-programmed linearization curves


Linearization tables for calculating the volume in the following vessels are preprogrammed into the device:

- Pyramid bottom
- Conical bottom
- Angled bottom
- Horizontal cylinder
- Sphere

Other linearization tables of up to 32 value pairs can be entered manually.

## Load

### 4 to 20 mA HART



A0039232

- 1 Power supply 10.5 to 30 VDC Ex i
- 2 Power supply 10.5 to 35 VDC, for other types of protection and non-certified device versions
- 3  $R_{L,max}$  maximum load resistance
- U Supply voltage



Operation via handheld terminal or PC with operating program: take minimum communication resistor of 250 Ω into consideration.

## Protocol-specific data

**HART****Manufacturer ID:**

17 (0x11{hex})

**Device type ID:**

0x11C1

**Device revision:**

1

**HART specification:**

7

**DD version:**

1

**Device description files (DTM, DD)**

Information and files available at:

■ [www.endress.com](http://www.endress.com)

On the product page for the device: Documents/Software → Device drivers

■ [www.fieldcommgroup.org](http://www.fieldcommgroup.org)**HART load:**

Min. 250 Ω

*HART device variables*

The following measured values are assigned to the device variables at the factory:

Device variable	Measured value
Assign PV (The PV is always applied to the current output)	Level linearized
Assign SV	Distance
Assign TV	Absolute echo amplitude
Assign QV	Relative echo amplitude

*Choice of HART device variables*

- Level linearized
- Distance
- Terminal voltage
- Electronics temperature
- Sensor temperature
- Absolute echo amplitude
- Relative echo amplitude
- Area of incoupling
- Percent of range
- Loop current
- Terminal current
- Not used
- Build-up index, optional (Guidance → Heartbeat Technology → Build-up detection → Configuration → Build-up index)
- **Build-up detection** parameter, optional (Guidance → Heartbeat Technology → Build-up detection → Configuration → Build-up detection)
- **Foam index** parameter, optional (Guidance → Heartbeat Technology → Foam detection → Configuration → Foam index)
- **Foam detection** parameter, optional (Guidance → Heartbeat Technology → Foam detection → Configuration → Foam detection)

*Supported functions*

- Burst mode
- Additional transmitter status
- Device locking

## Wireless HART data

**Minimum start-up voltage:**

10.5 V

**Start-up current:**

&lt; 3.6 mA

**Starting time:**

&lt; 15 s

**Minimum operating voltage:**

10.5 V


**Multidrop current:**


4 mA

**Time to establish connection:**

&lt; 30 s

## Power supply

**Terminal assignment****Single compartment housing**

 4 Connection terminals and ground terminal in the connection compartment


1 Positive terminal

2 Negative terminal


3 Internal ground terminal



### Dual compartment housing




A0042803


 5 Connection terminals and ground terminal in the connection compartment

- 1 Positive terminal
- 2 Negative terminal
- 3 Internal ground terminal

### Dual compartment housing, L-form



A0045842

 6 Connection terminals and ground terminal in the connection compartment

- 1 Positive terminal
- 2 Negative terminal
- 3 Internal ground terminal

### Terminals

- Supply voltage and internal ground terminal: 0.5 to 2.5 mm<sup>2</sup> (20 to 14 AWG)
- External ground terminal: 0.5 to 4 mm<sup>2</sup> (20 to 12 AWG)


### Available device plugs



In the case of devices with a plug, it is not necessary to open the housing for connection purposes.

Use the enclosed seals to prevent the penetration of moisture into the device.


Devices with M12 plug



- 7 View of the plug-in connection on the device
- 1 Signal +
  - 2 Not assigned
  - 3 Signal -
  - 4 Ground

Various M12 sockets are available as accessories for devices with M12 plugs.

Measuring devices with Harting plug Han7D



- A Electrical connection for devices with Harting plug Han7D
- B View of the plug-in connection on the device
- Brown
  - Green/yellow
  - + Blue

**Material**  
CuZn, gold-plated plug-in jack and plug contacts


**Supply voltage** The supply voltage depends on the selected type of device approval

Non-hazardous, Ex d, Ex e	10.5 to 35 V <sub>DC</sub>
Ex i	10.5 to 30 V <sub>DC</sub>
Nominal current	4 to 20 mA

**i** The power unit must be tested to ensure it meets safety requirements (e.g., PELV, SELV, Class 2) and complies with the relevant protocol specifications.

A suitable circuit breaker must be provided for the device in accordance with IEC/EN61010-1

**Potential equalization** The protective ground on the device must not be connected. If necessary, the potential matching line can be connected to the outer ground terminal of the transmitter before the device is connected.



A0046583

- A Single compartment housing, plastic  
 B Single compartment housing, aluminum  
 C Single compartment housing, 316L hygiene (Ex device)  
 D Dual compartment housing  
 E Dual compartment housing, L-form  
 1 Ground terminal for connecting the potential matching line

### WARNING

#### Explosion Hazard!


- Please refer to the separate documentation on applications in hazardous areas for the safety instructions.



For optimum electromagnetic compatibility:

- Keep the potential matching line as short as possible
- Observe a cross-section of at least 2.5 mm<sup>2</sup> (14 AWG)

### Cable entries



A0046584

- A Single compartment housing, plastic  
 B Single compartment housing, aluminum  
 C Single compartment housing, 316L hygiene  
 D Dual compartment housing  
 E Dual compartment housing, L-form  
 1 Cable entry  
 2 Dummy plug

The type of cable entry depends on the device version ordered.



Always route connecting cables downwards so that moisture cannot penetrate the connection compartment.

If necessary, create a drip loop or use a weather protection cover.

### Cable specification

#### Rated cross-section

- Supply voltage  
0.5 to 2.5 mm<sup>2</sup> (20 to 13 AWG)
- Protective earth or grounding of the cable shield  
> 1 mm<sup>2</sup> (17 AWG)
- External ground terminal  
0.5 to 4 mm<sup>2</sup> (20 to 12 AWG)

**Cable outer diameter**

The cable outer diameter depends on the cable gland used

- Coupling, plastic:  
Ø5 to 10 mm (0.2 to 0.38 in)
- Coupling, nickel-plated brass:  
Ø7 to 10.5 mm (0.28 to 0.41 in)
- Coupling, stainless steel:  
Ø7 to 12 mm (0.28 to 0.47 in)

**Overvoltage protection**

The overvoltage protection can optionally be ordered as a "Mounted accessory" via the product structure

**Devices without optional overvoltage protection**

The equipment fulfills the requirements of the product standard IEC / DIN EN 61326-1 (Table 2 Industrial Environment).

Depending on the type of port (DC power supply, input/output port) different testing levels according to IEC / DIN EN 61326-1 against transient overvoltages (Surge) are applied (IEC / DIN EN 61000-4-5 Surge):

Test level on DC power ports and input/output ports is 1 000 V line to earth

**Devices with optional overvoltage protection**

- Spark-over voltage: min. 400 V<sub>DC</sub>
- Tested according to IEC / DIN EN 60079-14 sub chapter 12.3 (IEC / DIN EN 60060-1 chapter 7)
- Nominal discharge current: 10 kA

**NOTICE****Device could be destroyed**

- Always ground device with integrated overvoltage protection.

**Overvoltage category**

Overvoltage category II

## Performance characteristics

**Reference operating conditions**

- Temperature = +24 °C (+75 °F) ±5 °C (±9 °F)
- Pressure = 960 mbar abs. (14 psia) ±100 mbar (±1.45 psi)
- Humidity = 60 % ±15 %
- Reflector: metal plate with diameter ≥ 1 m (40 in)
- No major interference reflections inside the signal beam

**Maximum measured error****Reference accuracy****Accuracy**

The accuracy is the sum of the non-linearity, non-repeatability and hysteresis.

- Measuring distance up to 0.8 m (2.62 ft): max. ±4 mm (±0.16 in)
- Measuring distance > 0.8 m (2.62 ft): ±1 mm (±0.04 in)


**Non-repeatability**

Non-repeatability is already included in the accuracy.  
≤ 1 mm (0.04 in)



If conditions deviate from the reference operating conditions, the offset/zero point that results from the installation conditions can be up to ±4 mm (±0.16 in). This additional offset/zero point can be eliminated by entering a correction (**Level correction** parameter) during commissioning.

Differing values in near-range applications



A0032636

8 Maximum measured error in near-range applications

$\Delta$  Maximum measured error  
 $R$  Reference point of the distance measurement  
 $D$  Distance from reference point of antenna

Measured value resolution	Dead band according to DIN EN IEC 61298-2 / DIN EN IEC 60770-1: <ul style="list-style-type: none"><li>■ Digital: 1 mm</li><li>■ Analog: 1 <math>\mu</math>A</li></ul>
Response time	<p>According to DIN EN IEC 61298-2 / DIN EN IEC 60770-1 , the step response time is the time following an abrupt change in the input signal up until the changed output signal has adopted 90 % of the steady-state value for the first time.</p> <p>The response time can be configured.</p> <p>The following step response times apply (in accordance with DIN EN IEC 61298-2 / DIN EN IEC 60770-1) when damping is switched off:</p> <ul style="list-style-type: none"><li>■ Pulse frequency <math>\geq 5</math>/s (cycle time <math>\leq 200</math> ms) at <math>U= 10.5</math> to <math>35</math> V, <math>I= 4</math> to <math>20</math> mA and <math>T_{amb}= -50</math> to <math>+80</math> °C (<math>-58</math> to <math>+176</math> °F)</li><li>■ Step response time <math>&lt; 1</math> s</li></ul>
Influence of ambient temperature	<p>The output changes due to the effect of the ambient temperature with respect to the reference temperature.</p> <p>The measurements are performed according to DIN EN IEC 61298-3 / DIN EN IEC 60770-1</p> <p><b>Digital output (HART)</b> Average <math>T_C = 2</math> mm/10 K</p> <p><b>Analog (current output)</b></p> <ul style="list-style-type: none"><li>■ Zero point (4 mA): average <math>T_C = 0.02</math> %/10 K</li><li>■ Span (20 mA): average <math>T_C = 0.05</math> %/10 K</li></ul>
Influence of gas phase	<p>High pressure reduces the speed of propagation of the measuring signals in the gas/vapor above the medium. This effect depends on the type of gas phase and its temperature. This results in a systematic measured error that increases with increasing distance between the reference point of the measurement (flange) and the surface of the product. The following table shows this measured</p>

error for some typical gases/vapors (with regard to the distance, a positive value means that an excessively large distance is measured):


Measured error for some typical gases/vapors

Gas phase	Temperature	Pressure		
		1 bar (14.5 psi)	10 bar (145 psi)	25 bar (362 psi)
Air/nitrogen	+20 °C (+68 °F)	0.00 %	+0.22 %	+0.58 %
	+200 °C (+392 °F)	-0.01 %	+0.13 %	+0.36 %
	+400 °C (+752 °F)	-0.02 %	+0.08 %	+0.29 %
Hydrogen	+20 °C (+68 °F)	-0.01 %	+0.10 %	+0.25 %
	+200 °C (+392 °F)	-0.02 %	+0.05 %	+0.17 %
	+400 °C (+752 °F)	-0.02 %	+0.03 %	+0.11 %
Water (saturated steam)	+100 °C (+212 °F)	+0.02 %	-	-
	+180 °C (+356 °F)	-	+2.10 %	-
	+263 °C (+505 °F)	-	-	+4.15 %
	+310 °C (+590 °F)	-	-	-
	+364 °C (+687 °F)	-	-	-

**i** With a known, constant pressure, it is possible to compensate for this measured error with a linearization, for example.

Mounting

Mounting location




A0016882

- A    Recommended distance from wall to nozzle outer edge ~ 1/6 of the vessel diameter. The device should never be mounted closer than 15 cm (5.91 in) to the tank wall.
- 1    Use of a weather protection cover; protection from direct sunlight or rain
- 2    Installation in the center, interference can cause signal loss
- 3    Do not install above the filling curtain

## Orientation


### Internal vessel fittings



A0031777

Avoid internal fittings (point level switches, temperature sensors, struts, vacuum rings, heating coils, baffles etc.) inside the signal beam. Pay attention to the beam angle  $\alpha$ .

### Avoiding interference echoes



A0031813

Metal deflector plates, installed at an angle to scatter the radar signals, help prevent interference echoes.

### Vertical alignment of antenna axis

Align the antenna so that it is perpendicular to the product surface.



The maximum reach of the antenna can be reduced, or additional interference signals can occur, if the antenna is not installed perpendicular to the product.


**Radial alignment of the antenna**

Based on the directional characteristic, radial alignment of the antenna is not necessary.

**Installation instructions****Integrated antenna, PEEK 20 mm (0.75 in)***Information about the mounting nozzle*

The maximum nozzle length  $H_{max}$  depends on the nozzle diameter  $D$ .

Maximum nozzle length  $H_{max}$  as a function of the nozzle diameter  $D$

	$\phi D$	$H_{max}$
	40 to 50 mm (1.6 to 2 in)	200 mm (8 in)
	50 to 80 mm (2 to 3.2 in)	300 mm (12 in)
	80 to 100 mm (3.2 to 4 in)	450 mm (18 in)
	100 to 150 mm (4 to 6 in)	550 mm (22 in)
	$\geq 150$ mm (6 in)	850 mm (34 in)



In the case of longer nozzles, reduced measuring performance must be expected.


Please note the following:

- The end of the nozzle must be smooth and free from burrs.
- The edge of the nozzle should be rounded.
- Mapping must be performed.
- Please contact the manufacturer's support department for applications with nozzles that are higher than indicated in the table.

**Antenna, PTFE clad, flush mount 50 mm (2 in)***Information about the mounting nozzle*

The maximum nozzle length  $H_{max}$  depends on the nozzle diameter  $D$ .

The maximum length of the nozzle  $H_{max}$  depends on the nozzle diameter  $D$

	$\phi D$	$H_{max}$
	50 to 80 mm (2 to 3.2 in)	600 mm (24 in)
	80 to 100 mm (3.2 to 4 in)	1 000 mm (40 in)
	100 to 150 mm (4 to 6 in)	1 250 mm (50 in)
	$\geq 150$ mm (6 in)	1 850 mm (74 in)



In the case of longer nozzles, reduced measuring performance must be expected.

Please note the following:


- The end of the nozzle must be smooth and free from burrs.
- The edge of the nozzle should be rounded.
- Mapping must be performed.
- Please contact the manufacturer's support department for applications with nozzles that are higher than indicated in the table.


**Antenna, PTFE clad, flush mount 80 mm (3 in)***Information about the mounting nozzle*

The maximum nozzle length  $H_{max}$  depends on the nozzle diameter  $D$ .



The maximum length of the nozzle  $H_{max}$  depends on the nozzle diameter  $D$

	$\phi D$	$H_{max}$
	80 to 100 mm (3.2 to 4 in)	1 750 mm (70 in)
	100 to 150 mm (4 to 6 in)	2 200 mm (88 in)
	$\geq 150$ mm (6 in)	3 300 mm (132 in)


 In the case of longer nozzles, reduced measuring performance must be expected.

Please note the following:


- The end of the nozzle must be smooth and free from burrs.
- The edge of the nozzle should be rounded.
- Mapping must be performed.
- Please contact the manufacturer's support department for applications with nozzles that are higher than indicated in the table.

**Beam angle**

The beam angle is defined as the angle  $\alpha$  where the energy density of the radar waves reaches half the value of the maximum energy density (3 dB width). Microwaves are also emitted outside the signal beam and can be reflected off interfering installations.




A0031824


 9 Relationship between beam angle  $\alpha$ , distance  $D$  and beamwidth diameter  $W$

 The beamwidth diameter  $W$  depends on the beam angle  $\alpha$  and the distance  $D$ .


Integrated antenna, PEEK 20 mm / 3/4",  $\alpha$  14 °

$W = D \times 0.26$	$D$	$W$
	5 m (16 ft)	1.23 m (4.04 ft)
	10 m (33 ft)	2.46 m (8.07 ft)

PTFE cladded, flush mount 50 mm (2 in) antenna,  $\alpha$  7 °


$W = D \times 0.12$	D	W
	5 m (16 ft)	0.61 m (2.00 ft)
	10 m (33 ft)	1.22 m (4.00 ft)
	15 m (49 ft)	1.83 m (6.00 ft)
	20 m (66 ft)	2.44 m (8.01 ft)
	25 m (82 ft)	3.05 m (10.01 ft)
	30 m (98 ft)	3.66 m (12.01 ft)
	35 m (115 ft)	4.27 m (14.01 ft)
	40 m (131 ft)	4.88 m (16.01 ft)
	45 m (148 ft)	5.50 m (18.04 ft)
	50 m (164 ft)	6.11 m (20.05 ft)

PTFE cladded, flush mount 80 mm (3 in) antenna,  $\alpha$  3 °

$W = D \times 0.05$	D	W
	5 m (16 ft)	0.25 m (0.82 ft)
	10 m (33 ft)	0.50 m (1.64 ft)
	15 m (49 ft)	0.75 m (2.46 ft)
	20 m (66 ft)	1.00 m (3.28 ft)
	25 m (82 ft)	1.25 m (4.10 ft)
	30 m (98 ft)	1.50 m (4.92 ft)
	35 m (115 ft)	1.75 m (5.74 ft)
	40 m (131 ft)	2.00 m (6.56 ft)
	45 m (148 ft)	2.25 m (7.38 ft)
	50 m (164 ft)	2.50 m (8.20 ft)
	60 m (197 ft)	3.00 m (9.84 ft)
	70 m (230 ft)	3.50 m (11.48 ft)
	80 m (262 ft)	4.00 m (13.12 ft)

### Special mounting instructions

#### Measurement through a ball valve



A0034564

- Measurements can be performed through an open full bore ball valve without any problems.
- At the transitions, no gap exceeding 1 mm (0.04 in) may be left.
- Opening diameter of ball valve must always correspond to the pipe diameter; avoid edges and constrictions.

#### External measurement through plastic cover or dielectric windows

- Dielectric constant of medium:  $\epsilon_r \geq 10$
- The distance from the tip of the antenna to the tank should be approx. 100 mm (4 in).
- Avoid installation positions where condensate or buildup can form between the antenna and the vessel
- In the case of outdoor installations, ensure that the area between the antenna and the tank is protected from the weather
- Do not install any fittings or attachments between the antenna and the tank that could reflect the signal


The thickness of the tank ceiling or the dielectric window depends on the  $\epsilon_r$  of the material.

The material thickness can be a full multiple of the optimum thickness (table); it is important to note, however, that the microwave transparency decreases significantly with increasing material thickness.

#### Optimum material thickness

Material	Optimum material thickness
PE; $\epsilon_r$ 2.3	1.25 mm (0.049 in)
PTFE; $\epsilon_r$ 2.1	1.30 mm (0.051 in)
PP; $\epsilon_r$ 2.3	1.25 mm (0.049 in)
Perspex; $\epsilon_r$ 3.1	1.10 mm (0.043 in)

#### Container with heat insulation



A0046566

If process temperatures are high, the device should be included in the usual container insulation system (2) to prevent the electronics from heating as a result of thermal radiation or convection. The rib structure (1) must not be insulated.

## Environment

### Ambient temperature range

The following values apply up to a process temperature of +85 °C (+185 °F). At higher process temperatures, the permitted ambient temperature is reduced.

- Without LCD display:
  - Standard: -40 to +85 °C (-40 to +185 °F)
  - Optionally available: -50 to +85 °C (-58 to +185 °F) with restricted operating life and performance
  - Optionally available: -60 to +85 °C (-76 to +185 °F) with restricted operating life and performance; below -50 °C (-58 °F): devices can be damaged permanently
- With LCD display: -40 to +85 °C (-40 to +185 °F) with limitations in optical properties such as display speed and contrast. Can be used without limitations up to -20 to +60 °C (-4 to +140 °F)



If operating outdoors in strong sunlight:

- Mount the device in the shade.
- Avoid direct sunlight, particularly in warm climatic regions.
- Use a weather protection cover (see accessories).

### Ambient temperature limits

The permitted ambient temperature ( $T_a$ ) depends on the selected housing material (Product Configurator → Housing; Material →) and the selected process temperature range (Product Configurator → Application →).


In the event of temperature ( $T_p$ ) at the process connection, the permitted ambient temperature ( $T_a$ ) is reduced.



The following information only takes functional aspects into consideration. Additional restrictions may apply for certified device versions.

### Plastic housing

*Plastic housing; process temperature -10 to +150 °C (+14 to +302 °F)*



A0032024


10 Plastic housing; process temperature -10 to +150 °C (+14 to +302 °F)

P1	=	$T_p$ :	-10 °C (+14 °F)		$T_a$ :	+76 °C (+169 °F)
P2	=	$T_p$ :	+76 °C (+169 °F)		$T_a$ :	+76 °C (+169 °F)
P3	=	$T_p$ :	+150 °C (+302 °F)		$T_a$ :	+25 °C (+77 °F)
P4	=	$T_p$ :	+150 °C (+302 °F)		$T_a$ :	-10 °C (+14 °F)
P5	=	$T_p$ :	-10 °C (+14 °F)		$T_a$ :	-10 °C (+14 °F)



The selected process temperature range is restricted from -10 to +150 °C (+14 to +302 °F) to 0 to +150 °C (+32 to +302 °F) in devices with a plastic housing and CSA C/US approval.

Process temperature restricted to 0 to +150 °C (+32 to +302 °F) for CSA C/US approval and plastic housing




A0048826

**11** Plastic housing; process temperature 0 to +150 °C (+32 to +302 °F) for CSA C/US approval

P1	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : +76 °C (+169 °F)
P2	=	$T_p$ : +76 °C (+169 °F)		$T_a$ : +76 °C (+169 °F)
P3	=	$T_p$ : +150 °C (+302 °F)		$T_a$ : +25 °C (+77 °F)
P4	=	$T_p$ : +150 °C (+302 °F)		$T_a$ : 0 °C (+32 °F)
P5	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : 0 °C (+32 °F)

Plastic housing; process temperature -10 to +200 °C (+14 to +392 °F)



A0032024


**12** Plastic housing; process temperature -10 to +200 °C (+14 to +392 °F)

P1	=	$T_p$ : -10 °C (+14 °F)		$T_a$ : +76 °C (+169 °F)
P2	=	$T_p$ : +76 °C (+169 °F)		$T_a$ : +76 °C (+169 °F)
P3	=	$T_p$ : +200 °C (+392 °F)		$T_a$ : +27 °C (+81 °F)
P4	=	$T_p$ : +200 °C (+392 °F)		$T_a$ : -10 °C (+14 °F)
P5	=	$T_p$ : -10 °C (+14 °F)		$T_a$ : -10 °C (+14 °F)



The selected process temperature range is restricted from -10 to +200 °C (+14 to +392 °F) to 0 to +200 °C (+32 to +392 °F) in devices with a plastic housing and CSA C/US approval.

Process temperature restricted to 0 to +200 °C (+32 to +392 °F) for CSA C/US approval and plastic housing




A0048826

**13** Plastic housing; process temperature 0 to +200 °C (+32 to +392 °F) for CSA C/US approval

P1	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : +76 °C (+169 °F)
P2	=	$T_p$ : +76 °C (+169 °F)		$T_a$ : +76 °C (+169 °F)
P3	=	$T_p$ : +200 °C (+392 °F)		$T_a$ : +27 °C (+81 °F)
P4	=	$T_p$ : +200 °C (+392 °F)		$T_a$ : 0 °C (+32 °F)
P5	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : 0 °C (+32 °F)

Plastic housing; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)




A0032024

14 Plastic housing; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)

P1	=	$T_p$ :	$-20$ °C ( $-4$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P2	=	$T_p$ :	$+76$ °C ( $+169$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P3	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$+25$ °C ( $+77$ °F)
P4	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$-20$ °C ( $-4$ °F)
P5	=	$T_p$ :	$-20$ °C ( $-4$ °F)		$T_a$ :	$-20$ °C ( $-4$ °F)

**i** In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F) is limited to  $0$  to  $+150$  °C ( $+32$  to  $+302$  °F).

Restriction to a process temperature of  $0$  to  $+150$  °C ( $+32$  to  $+302$  °F) with CSA C/US approval and plastic housing




A0049826

15 Plastic housing; process temperature  $0$  to  $+150$  °C ( $+32$  to  $+302$  °F) with CSA C/US approval

P1	=	$T_p$ :	$0$ °C ( $+32$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P2	=	$T_p$ :	$+76$ °C ( $+169$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P3	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$+25$ °C ( $+77$ °F)
P4	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$0$ °C ( $+32$ °F)
P5	=	$T_p$ :	$0$ °C ( $+32$ °F)		$T_a$ :	$0$ °C ( $+32$ °F)

Plastic housing; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)




A0032024

16 Plastic housing; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)

P1	=	$T_p$ :	$-20$ °C ( $-4$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P2	=	$T_p$ :	$+76$ °C ( $+169$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P3	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$+27$ °C ( $+81$ °F)
P4	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$-20$ °C ( $-4$ °F)
P5	=	$T_p$ :	$-20$ °C ( $-4$ °F)		$T_a$ :	$-20$ °C ( $-4$ °F)

**i** In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F) is limited to  $0$  to  $+200$  °C ( $+32$  to  $+392$  °F).

Restriction to a process temperature of 0 to +200 °C (+32 to +392 °F) with CSA C/US approval and plastic housing




A0048826

17 Plastic housing; process temperature 0 to +200 °C (+32 to +392 °F) with CSA C/US approval

P1	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : +76 °C (+169 °F)
P2	=	$T_p$ : +76 °C (+169 °F)		$T_a$ : +76 °C (+169 °F)
P3	=	$T_p$ : +200 °C (+392 °F)		$T_a$ : +27 °C (+81 °F)
P4	=	$T_p$ : +200 °C (+392 °F)		$T_a$ : 0 °C (+32 °F)
P5	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : 0 °C (+32 °F)

Plastic housing; process temperature -40 to +150 °C (-40 to +302 °F)



A0032024


18 Plastic housing; process temperature -40 to +150 °C (-40 to +302 °F)

P1	=	$T_p$ : -40 °C (-40 °F)		$T_a$ : +76 °C (+169 °F)
P2	=	$T_p$ : +76 °C (+169 °F)		$T_a$ : +76 °C (+169 °F)
P3	=	$T_p$ : +150 °C (+302 °F)		$T_a$ : +25 °C (+77 °F)
P4	=	$T_p$ : +150 °C (+302 °F)		$T_a$ : -40 °C (-40 °F)
P5	=	$T_p$ : -40 °C (-40 °F)		$T_a$ : -40 °C (-40 °F)



In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of -40 to +150 °C (-40 to +302 °F) is limited to 0 to +150 °C (+32 to +302 °F).

Restriction to a process temperature of 0 to +150 °C (+32 to +302 °F) with CSA C/US approval and plastic housing




A0048826

19 Plastic housing; process temperature 0 to +150 °C (+32 to +302 °F) with CSA C/US approval

P1	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : +76 °C (+169 °F)
P2	=	$T_p$ : +76 °C (+169 °F)		$T_a$ : +76 °C (+169 °F)
P3	=	$T_p$ : +150 °C (+302 °F)		$T_a$ : +25 °C (+77 °F)
P4	=	$T_p$ : +150 °C (+302 °F)		$T_a$ : 0 °C (+32 °F)
P5	=	$T_p$ : 0 °C (+32 °F)		$T_a$ : 0 °C (+32 °F)

Plastic housing; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)




A0032024

20 Plastic housing; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)

P1	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P2	=	$T_p$ :	$+76$ °C ( $+169$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P3	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$+27$ °C ( $+81$ °F)
P4	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)
P5	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)

**i** In the case of devices with a plastic housing and CSA C/US approval, the selected process temperature of  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F) is limited to  $0$  to  $+200$  °C ( $+32$  to  $+392$  °F).

Restriction to a process temperature of  $0$  to  $+200$  °C ( $+32$  to  $+392$  °F) with CSA C/US approval and plastic housing




A0049826

21 Plastic housing; process temperature  $0$  to  $+200$  °C ( $+32$  to  $+392$  °F) with CSA C/US approval

P1	=	$T_p$ :	$0$ °C ( $+32$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P2	=	$T_p$ :	$+76$ °C ( $+169$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P3	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$+27$ °C ( $+81$ °F)
P4	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$0$ °C ( $+32$ °F)
P5	=	$T_p$ :	$0$ °C ( $+32$ °F)		$T_a$ :	$0$ °C ( $+32$ °F)

### Aluminum housing, coated

Aluminum housing; process temperature  $-10$  to  $+150$  °C ( $+14$  to  $+302$  °F)




A0032024

22 Aluminum housing, coated; process temperature  $-10$  to  $+150$  °C ( $+14$  to  $+302$  °F)

P1	=	$T_p$ :	$-10$ °C ( $+14$ °F)		$T_a$ :	$+79$ °C ( $+174$ °F)
P2	=	$T_p$ :	$+79$ °C ( $+174$ °F)		$T_a$ :	$+79$ °C ( $+174$ °F)
P3	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$+53$ °C ( $+127$ °F)
P4	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$-10$ °C ( $+14$ °F)
P5	=	$T_p$ :	$-10$ °C ( $+14$ °F)		$T_a$ :	$-10$ °C ( $+14$ °F)



Aluminum housing; process temperature  $-10$  to  $+200$  °C ( $+14$  to  $+392$  °F)




A0032024

23 Aluminum housing, coated; process temperature  $-10$  to  $+200$  °C ( $+14$  to  $+392$  °F)

P1	=	$T_p$ : $-10$ °C ( $+14$ °F)		$T_a$ : $+79$ °C ( $+174$ °F)
P2	=	$T_p$ : $+79$ °C ( $+174$ °F)		$T_a$ : $+79$ °C ( $+174$ °F)
P3	=	$T_p$ : $+200$ °C ( $+392$ °F)		$T_a$ : $+47$ °C ( $+117$ °F)
P4	=	$T_p$ : $+200$ °C ( $+392$ °F)		$T_a$ : $-10$ °C ( $+14$ °F)
P5	=	$T_p$ : $-10$ °C ( $+14$ °F)		$T_a$ : $-10$ °C ( $+14$ °F)

Aluminum housing; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)




A0032024

24 Aluminum housing, coated; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)

P1	=	$T_p$ : $-20$ °C ( $-4$ °F)		$T_a$ : $+79$ °C ( $+174$ °F)
P2	=	$T_p$ : $+79$ °C ( $+174$ °F)		$T_a$ : $+79$ °C ( $+174$ °F)
P3	=	$T_p$ : $+150$ °C ( $+302$ °F)		$T_a$ : $+53$ °C ( $+127$ °F)
P4	=	$T_p$ : $+150$ °C ( $+302$ °F)		$T_a$ : $-20$ °C ( $-4$ °F)
P5	=	$T_p$ : $-20$ °C ( $-4$ °F)		$T_a$ : $-20$ °C ( $-4$ °F)

Aluminum housing; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)




A0032024

25 Aluminum housing, coated; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)

P1	=	$T_p$ : $-20$ °C ( $-4$ °F)		$T_a$ : $+79$ °C ( $+174$ °F)
P2	=	$T_p$ : $+79$ °C ( $+174$ °F)		$T_a$ : $+79$ °C ( $+174$ °F)
P3	=	$T_p$ : $+200$ °C ( $+392$ °F)		$T_a$ : $+47$ °C ( $+117$ °F)
P4	=	$T_p$ : $+200$ °C ( $+392$ °F)		$T_a$ : $-20$ °C ( $-4$ °F)
P5	=	$T_p$ : $-20$ °C ( $-4$ °F)		$T_a$ : $-20$ °C ( $-4$ °F)

Aluminum housing; process temperature  $-40$  to  $+150$  °C ( $-40$  to  $+302$  °F)




A0032024

26 Aluminum housing, coated; process temperature  $-40$  to  $+150$  °C ( $-40$  to  $+302$  °F)

P1	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$+79$ °C ( $+174$ °F)
P2	=	$T_p$ :	$+79$ °C ( $+174$ °F)		$T_a$ :	$+79$ °C ( $+174$ °F)
P3	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$+53$ °C ( $+127$ °F)
P4	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)
P5	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)

Aluminum housing; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)




A0032024

27 Aluminum housing, coated; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)

P1	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$+79$ °C ( $+174$ °F)
P2	=	$T_p$ :	$+79$ °C ( $+174$ °F)		$T_a$ :	$+79$ °C ( $+174$ °F)
P3	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$+47$ °C ( $+117$ °F)
P4	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)
P5	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)

### 316L housing

316L housing; process temperature  $-10$  to  $+150$  °C ( $+14$  to  $+302$  °F)




A0032024

28 316L housing; process temperature  $-10$  to  $+150$  °C ( $+14$  to  $+302$  °F)

P1	=	$T_p$ :	$-10$ °C ( $+14$ °F)		$T_a$ :	$+77$ °C ( $+171$ °F)
P2	=	$T_p$ :	$+77$ °C ( $+171$ °F)		$T_a$ :	$+77$ °C ( $+171$ °F)
P3	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$+43$ °C ( $+109$ °F)
P4	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$-10$ °C ( $+14$ °F)
P5	=	$T_p$ :	$-10$ °C ( $+14$ °F)		$T_a$ :	$-10$ °C ( $+14$ °F)

316L housing; process temperature  $-10$  to  $+200$  °C ( $+14$  to  $+392$  °F)




A0032024

29 316L housing; process temperature  $-10$  to  $+200$  °C ( $+14$  to  $+392$  °F)

P1	=	$T_p: -10$ °C ( $+14$ °F)		$T_a: +77$ °C ( $+171$ °F)
P2	=	$T_p: +77$ °C ( $+171$ °F)		$T_a: +77$ °C ( $+171$ °F)
P3	=	$T_p: +200$ °C ( $+392$ °F)		$T_a: +38$ °C ( $+100$ °F)
P4	=	$T_p: +200$ °C ( $+392$ °F)		$T_a: -10$ °C ( $+14$ °F)
P5	=	$T_p: -10$ °C ( $+14$ °F)		$T_a: -10$ °C ( $+14$ °F)

316L housing; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)




A0032024

30 316L housing; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)

P1	=	$T_p: -20$ °C ( $-4$ °F)		$T_a: +77$ °C ( $+171$ °F)
P2	=	$T_p: +77$ °C ( $+171$ °F)		$T_a: +77$ °C ( $+171$ °F)
P3	=	$T_p: +150$ °C ( $+302$ °F)		$T_a: +43$ °C ( $+109$ °F)
P4	=	$T_p: +150$ °C ( $+302$ °F)		$T_a: -20$ °C ( $-4$ °F)
P5	=	$T_p: -20$ °C ( $-4$ °F)		$T_a: -20$ °C ( $-4$ °F)

316L housing; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)




A0032024

31 316L housing; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)

P1	=	$T_p: -20$ °C ( $-4$ °F)		$T_a: +77$ °C ( $+171$ °F)
P2	=	$T_p: +77$ °C ( $+171$ °F)		$T_a: +77$ °C ( $+171$ °F)
P3	=	$T_p: +200$ °C ( $+392$ °F)		$T_a: +38$ °C ( $+100$ °F)
P4	=	$T_p: +200$ °C ( $+392$ °F)		$T_a: -20$ °C ( $-4$ °F)
P5	=	$T_p: -20$ °C ( $-4$ °F)		$T_a: -20$ °C ( $-4$ °F)

316L housing; process temperature  $-40$  to  $+150$  °C ( $-40$  to  $+302$  °F)




A0032024

32 316L housing; process temperature range:  $-40$  to  $+150$  °C ( $-40$  to  $+302$  °F)

$P1 = T_p: -40$  °C ( $-40$  °F) |  $T_a: +77$  °C ( $+171$  °F)  
 $P2 = T_p: +77$  °C ( $+171$  °F) |  $T_a: +77$  °C ( $+171$  °F)  
 $P3 = T_p: +150$  °C ( $+302$  °F) |  $T_a: +43$  °C ( $+109$  °F)  
 $P4 = T_p: +150$  °C ( $+302$  °F) |  $T_a: -40$  °C ( $-40$  °F)  
 $P5 = T_p: -40$  °C ( $-40$  °F) |  $T_a: -40$  °C ( $-40$  °F)

316L housing; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)




A0032024

33 316L housing; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)

$P1 = T_p: -40$  °C ( $-40$  °F) |  $T_a: +77$  °C ( $+171$  °F)  
 $P2 = T_p: +77$  °C ( $+171$  °F) |  $T_a: +77$  °C ( $+171$  °F)  
 $P3 = T_p: +200$  °C ( $+392$  °F) |  $T_a: +38$  °C ( $+100$  °F)  
 $P4 = T_p: +200$  °C ( $+392$  °F) |  $T_a: -40$  °C ( $-40$  °F)  
 $P5 = T_p: -40$  °C ( $-40$  °F) |  $T_a: -40$  °C ( $-40$  °F)

### 316L housing, hygiene

316L housing, hygiene; process temperature  $-10$  to  $+150$  °C ( $+14$  to  $+302$  °F)




A0032024

34 316L housing, hygiene; process temperature  $-10$  to  $+150$  °C ( $+14$  to  $+302$  °F)

$P1 = T_p: -10$  °C ( $+14$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P2 = T_p: +76$  °C ( $+169$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P3 = T_p: +150$  °C ( $+302$  °F) |  $T_a: +41$  °C ( $+106$  °F)  
 $P4 = T_p: +150$  °C ( $+302$  °F) |  $T_a: -10$  °C ( $+14$  °F)  
 $P5 = T_p: -10$  °C ( $+14$  °F) |  $T_a: -10$  °C ( $+14$  °F)

316L housing, hygiene; process temperature  $-10$  to  $+200$  °C ( $+14$  to  $+392$  °F)




A0032024

35 316L housing, hygiene; process temperature  $-10$  to  $+200$  °C ( $+14$  to  $+392$  °F)

$P1 = T_p: -10$  °C ( $+14$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P2 = T_p: +76$  °C ( $+169$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P3 = T_p: +200$  °C ( $+392$  °F) |  $T_a: +32$  °C ( $+90$  °F)  
 $P4 = T_p: +200$  °C ( $+392$  °F) |  $T_a: -10$  °C ( $+14$  °F)  
 $P5 = T_p: -10$  °C ( $+14$  °F) |  $T_a: -10$  °C ( $+14$  °F)

316L housing, hygiene; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)




A0032024

36 316L housing, hygiene; process temperature  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)

$P1 = T_p: -20$  °C ( $-4$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P2 = T_p: +76$  °C ( $+169$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P3 = T_p: +150$  °C ( $+302$  °F) |  $T_a: +41$  °C ( $+106$  °F)  
 $P4 = T_p: +150$  °C ( $+302$  °F) |  $T_a: -20$  °C ( $-4$  °F)  
 $P5 = T_p: -20$  °C ( $-4$  °F) |  $T_a: -20$  °C ( $-4$  °F)

316L housing, hygiene; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)




A0032024

37 316L housing, hygiene; process temperature  $-20$  to  $+200$  °C ( $-4$  to  $+392$  °F)

$P1 = T_p: -20$  °C ( $-4$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P2 = T_p: +76$  °C ( $+169$  °F) |  $T_a: +76$  °C ( $+169$  °F)  
 $P3 = T_p: +200$  °C ( $+392$  °F) |  $T_a: +32$  °C ( $+90$  °F)  
 $P4 = T_p: +200$  °C ( $+392$  °F) |  $T_a: -20$  °C ( $-4$  °F)  
 $P5 = T_p: -20$  °C ( $-4$  °F) |  $T_a: -20$  °C ( $-4$  °F)

316L housing, hygiene; process temperature  $-40$  to  $+150$  °C ( $-40$  to  $+302$  °F)




A0032024

38 316L housing, hygiene; process temperature range:  $-40$  to  $+150$  °C ( $-40$  to  $+302$  °F)

P1	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P2	=	$T_p$ :	$+76$ °C ( $+169$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P3	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$+41$ °C ( $+106$ °F)
P4	=	$T_p$ :	$+150$ °C ( $+302$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)
P5	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)

316L housing, hygiene; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)



A0032024

39 316L housing, hygiene; process temperature  $-40$  to  $+200$  °C ( $-40$  to  $+392$  °F)

P1	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P2	=	$T_p$ :	$+76$ °C ( $+169$ °F)		$T_a$ :	$+76$ °C ( $+169$ °F)
P3	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$+32$ °C ( $+90$ °F)
P4	=	$T_p$ :	$+200$ °C ( $+392$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)
P5	=	$T_p$ :	$-40$ °C ( $-40$ °F)		$T_a$ :	$-40$ °C ( $-40$ °F)

#### Storage temperature

- Without LCD display:  $-40$  to  $+90$  °C ( $-40$  to  $+194$  °F)
- With LCD display:  $-40$  to  $+85$  °C ( $-40$  to  $+185$  °F)

#### Climate class

DIN EN 60068-2-38 (test Z/AD)

#### Installation height as per IEC61010-1 Ed.3

- Generally up to 2 000 m (6 600 ft) above sea level
- Over 2 000 m (6 600 ft) under the following conditions:
  - Supply voltage  $< 35$  V<sub>DC</sub>
  - Power supply, overvoltage category 1

#### Degree of protection

Testing according to IEC 60529 and NEMA 250

#### Housing

IP66/68, NEMA Type 4X/6P

IP68 test condition: 1.83 m under water for 24 hours.

#### Cable entries

- M20 coupling, plastic, IP66/68 NEMA Type 4X/6P
- M20 coupling, nickel-plated brass, IP66/68 NEMA Type 4X/6P
- M20 coupling, 316L, IP66/68 NEMA Type 4X/6P
- M20 coupling, hygiene, IP66/68/69 NEMA Type 4X/6P
- M20 thread, IP66/68 NEMA Type 4X/6P
- G1/2 thread, IP66/68 NEMA Type 4X/6P

If the G1/2 thread is selected, the device is delivered with an M20 thread as standard and a G1/2 adapter is included with the delivery, along with the corresponding documentation

- NPT ½ thread, IP66/68 NEMA Type 4X/6P
- HAN7D plug, 90 degrees, IP65 NEMA Type 4X
- M12 plug
  - When housing is closed and connecting cable is plugged in: IP66/67 NEMA Type 4X
  - When housing is open or connecting cable is not plugged in: IP20, NEMA Type 1

**NOTICE****Plug M12 and plug HAN7D: incorrect mounting can invalidate the IP protection class!**

- ▶ The degree of protection only applies if the connecting cable used is plugged in and screwed tight.
- ▶ The degree of protection only applies if the connecting cable used is specified according to IP67 NEMA Type 4X.
- ▶ The protection classes are only maintained if the dummy cap is used or the cable is connected.

**Vibration resistance**DIN EN 60068-2-64 / IEC 60068-2-64 for 5 to 2 000 Hz: 1.5 (m/s<sup>2</sup>)/Hz**Electromagnetic compatibility (EMC)**

- Electromagnetic compatibility as per EN 61326 series and NAMUR recommendation EMC (NE21)
- With regard to the safety function (SIL), the requirements of EN 61326-3-x are satisfied
- Maximum measured error during EMC testing: < 0.5 % of the span.

For more details refer to the EU Declaration of Conformity.

## Process


**Process pressure range****WARNING**

The maximum pressure for the device depends on the lowest-rated component with regard to pressure (components are: process connection, optional mounted parts or accessories).

- ▶ Only operate the device within the specified limits for the components!
- ▶ MWP (Maximum Working Pressure): The MWP is specified on the nameplate. This value refers to a reference temperature of +20 °C (+68 °F) and may be applied to the device for an unlimited time. Note temperature dependence of MWP. For flanges, refer to the following standards for the permitted pressure values at higher temperatures: EN 1092-1 (with regard to their stability/temperature property, the materials 1.4435 and 1.4404 are grouped together under EN 1092-1; the chemical composition of the two materials can be identical), ASME B16.5, JIS B2220 (the latest version of the standard applies in each case). MWP data that deviate from this are provided in the relevant sections of the Technical Information.
- ▶ The Pressure Equipment Directive (2014/68/EU) uses the abbreviation **PS**. This corresponds to the maximum working pressure (MWP) of the device.

The following tables show the dependencies between the seal material, process temperature (T<sub>p</sub>) and process pressure range for each process connection that can be selected for the antenna used.


**Integrated antenna, PEEK, 20 mm (0.75 in)***Process connection M24 with process adapter, accessory enclosed*

	Seal	T <sub>p</sub>	Process pressure range
 A0048027	FKM Viton	-10 to +150 °C (+14 to +302 °F)	-1 to 20 bar (-14.5 to 290 psi)
	FKM Viton	-10 to +200 °C (+14 to +392 °F)	-1 to 20 bar (-14.5 to 290 psi)
	EPDM	-40 to +150 °C (-40 to +302 °F)	-1 to 20 bar (-14.5 to 290 psi)
	FFKM Kalrez	-20 to +150 °C (-4 to +302 °F)	-1 to 20 bar (-14.5 to 290 psi)
	FFKM Kalrez	-20 to +200 °C (-4 to +392 °F)	-1 to 20 bar (-14.5 to 290 psi)




The pressure range may be further restricted in the event of a CRN approval.


**Antenna, cladded flush mount, PTFE, 50 mm (2 in)***Process connection Tri-Clamp DN51 (2") ISO2852*

	Seal	T <sub>p</sub>	Process pressure range
 A0047838	PTFE cladded	-40 to +150 °C (-40 to +302 °F)	-1 to 16 bar (-14.5 to 232 psi)
	PTFE cladded	-40 to +200 °C (-40 to +392 °F)	-1 to 16 bar (-14.5 to 232 psi)

*Process connection Tri-Clamp DN70-76.1 (3") ISO2852*

	Seal	T <sub>p</sub>	Process pressure range
 A0047838	PTFE cladded	-40 to +150 °C (-40 to +302 °F)	-1 to 14 bar (-14.5 to 203 psi)
	PTFE cladded	-40 to +200 °C (-40 to +392 °F)	-1 to 14 bar (-14.5 to 203 psi)


*Process connection slotted nut DIN11851 DN50 PN25*

	Seal	T <sub>p</sub>	Process pressure range
 A0050063	PTFE cladded	-40 to +150 °C (-40 to +302 °F)	-1 to 25 bar (-14.5 to 362.6 psi)
	PTFE cladded	-40 to +200 °C (-40 to +392 °F)	-1 to 25 bar (-14.5 to 362.6 psi)




The pressure range may be further restricted in the event of a CRN approval.


**Antenna, cladded flush mount, PTFE, 80 mm (3 in)***Process connection Tri-Clamp DN101.6 (4") ISO2852*

	Seal	T <sub>p</sub>	Process pressure range
 A0047826	PTFE cladded	-40 to +150 °C (-40 to +302 °F)	-1 to 14 bar (-14.5 to 203 psi)
	PTFE cladded	-40 to +200 °C (-40 to +392 °F)	-1 to 14 bar (-14.5 to 203 psi)



Process connection slotted nut DIN11851 DN80 PN25

	Seal	T <sub>p</sub>	Process pressure range
 A0047825	PTFE cladded	-40 to +150 °C (-40 to +302 °F)	-1 to 25 bar (-14.5 to 362.6 psi)
	PTFE cladded	-40 to +200 °C (-40 to +392 °F)	-1 to 25 bar (-14.5 to 362.6 psi)


 The pressure range may be further restricted in the event of a CRN approval.

Dielectric constant


**For liquids**  
 $\epsilon_r \geq 1.2$   
Contact Endress+Hauser for applications with lower dielectric constants than indicated.


Mechanical construction

Dimensions


 The dimensions of the individual components must be added together for the total dimensions.

Single compartment housing, plastic



 40 Dimensions of single compartment housing, plastic (PBT). Unit of measurement mm (in)  
1 Height with cover comprising plastic sight glass  
2 Cover without sight glass

## Single compartment housing, aluminum




A0038380

41 Dimensions of single compartment housing, aluminum. Unit of measurement mm (in)

- 1 Height with cover comprising glass sight glass (devices for Ex d/XP, dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass

Single compartment housing, 316L hygiene




A0050364

42 Dimensions of single compartment housing, 316L hygiene. Unit of measurement mm (in)

- 1 Height with cover comprising glass sight glass (dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass

## Dual compartment housing, aluminum




A0038377

43 Dimensions of dual compartment housing, aluminum. Unit of measurement mm (in)


- 1 Height with cover comprising glass sight glass (devices for Ex d/XP, dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass

Dual compartment housing, L-shaped, aluminum or 316 L



44 Dimensions of L-shaped dual compartment housing. Unit of measurement mm (in)

- 1 Height with cover comprising glass sight glass (devices for Ex d/XP, dust Ex)
- 2 Height with cover comprising plastic sight glass
- 3 Cover without sight glass

**Integrated antenna, PEEK, 20 mm / M24×1.5**

A0046492

45 Dimensions of integrated antenna, PEEK, 20 mm / M24×1.5. Unit of measurement mm (in)

A Process temperature version ≤150 °C (302 °F)

B Process temperature version ≤200 °C (392 °F)


R Reference point of measurement

1 Bottom edge of housing

L1 127 mm (5.00 in); version with Ex d or XP approval +5 mm (+0.20 in)

L2 139 mm (5.47 in); version with Ex d or XP approval +5 mm (+0.20 in)


Antenna, cladded flush mount, PTFE, 50 mm (2 in), slotted nut DIN11851



46 Dimensions of antenna, cladded flush mount, PTFE, 50 mm (2 in), slotted nut DIN11851. Unit of measurement mm (in)

- A Process temperature version  $\leq 150^{\circ}\text{C}$  ( $302^{\circ}\text{F}$ )
- B Process temperature version  $\leq 200^{\circ}\text{C}$  ( $392^{\circ}\text{F}$ )
- R Reference point of measurement
- 1 Bottom edge of housing
- L1 118 mm (4.65 in); version with Ex d or XP approval +5 mm (+0.20 in)
- L2 130 mm (5.12 in); version with Ex d or XP approval +5 mm (+0.20 in)

**Antenna, cladded flush mount, PTFE, 80 mm (3 in), slotted nut DIN11851**



A0046497

47 Dimensions of antenna, cladded flush mount, PTFE, 80 mm (3 in), slotted nut DIN11851. Unit of measurement mm (in)

A Process temperature version  $\leq 150\text{ }^{\circ}\text{C}$  (302  $^{\circ}\text{F}$ )

B Process temperature version  $\leq 200\text{ }^{\circ}\text{C}$  (392  $^{\circ}\text{F}$ )

R Reference point of measurement


1 Bottom edge of housing

L1 159 mm (6.26 in); version with Ex d or XP approval +5 mm (+0.20 in)

L2 171 mm (6.73 in); version with Ex d or XP approval +5 mm (+0.20 in)



**Antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN40-51 (2") ISO2852**




**48** Dimensions of antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN51 (2") ISO2852.  
Unit of measurement mm (in)

- A Process temperature version  $\leq 150\text{ }^{\circ}\text{C}$  (302  $^{\circ}\text{F}$ )
- B Process temperature version  $\leq 200\text{ }^{\circ}\text{C}$  (392  $^{\circ}\text{F}$ )
- R Reference point of measurement
- 1 Bottom edge of housing
- L1 116 mm (4.57 in); version with Ex d or XP approval +5 mm (+0.20 in)
- L2 128 mm (5.04 in); version with Ex d or XP approval +5 mm (+0.20 in)

**i** Process connection suitable for  
DN51 nominal diameter and pipe inner diameter 48.6 mm (1.91 in)

**Antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN70-76.1 (3") ISO2852**



A0046484

49 Dimensions of antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp DN70-76.1 (3") ISO2852. Unit of measurement mm (in)

A Process temperature version  $\leq 150^\circ\text{C}$  (302  $^\circ\text{F}$ )

B Process temperature version  $\leq 200^\circ\text{C}$  (392  $^\circ\text{F}$ )

R Reference point of measurement

1 Bottom edge of housing


L1 116 mm (4.57 in); version with Ex d or XP approval +5 mm (+0.20 in)

L2 128 mm (5.04 in); version with Ex d or XP approval +5 mm (+0.20 in)



Process connection suitable for

- DN70 nominal diameter with pipe inner diameter 66.8 mm (2.63 in)
- DN76.1 nominal diameter with pipe inner diameter 72.9 mm (2.87 in)

**Antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp DN101.6 (4") ISO2852**

**50** Dimensions of antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp DN101.6 (4") ISO2852.  
Unit of measurement mm (in)

- A Process temperature version  $\leq 150\text{ }^{\circ}\text{C}$  (302  $^{\circ}\text{F}$ )  
 B Process temperature version  $\leq 200\text{ }^{\circ}\text{C}$  (392  $^{\circ}\text{F}$ )  
 R Reference point of measurement  
 1 Bottom edge of housing  
 L1 155 mm (6.10 in); version with Ex d or XP approval +5 mm (+0.20 in)  
 L2 167 mm (6.57 in); version with Ex d or XP approval +5 mm (+0.20 in)

**i** Process connection suitable for  
 DN101.6 nominal diameter with pipe inner diameter 97.6 mm (3.84 in)

**Weight**

**i** The weights of the individual components must be added together for the total weight.

**Housing**

Weight including electronics and display.

**Single compartment housing**

- Plastic: 0.5 kg (1.10 lb)
- Aluminum: 1.2 kg (2.65 lb)
- 316L hygiene: 1.2 kg (2.65 lb)

**Dual compartment housing**

Aluminum: 1.4 kg (3.09 lb)

**Dual compartment housing, L-form**

- Aluminum: 1.7 kg (3.75 lb)
- Stainless steel: 4.5 kg (9.9 lb)

**Antenna and process connection adapter**

**i** The flange weight (316/316L) depends on the selected standard and sealing surface.  
 Details -> TI00426F or in the relevant standard

**i** The heaviest version is indicated for the antenna weights

**Integrated antenna, PEEK, 20 mm (0.75 in)**

1.2 kg (2.65 lb)

**Antenna, cladded flush mount, PTFE, 50 mm (2 in)**

2.2 kg (4.85 lb) for process connection slotted nut DIN11851

**Antenna, cladded flush mount, PTFE, 80 mm (3 in)**

3.4 kg (7.50 lb) for process connection slotted nut DIN11851

**Materials****Materials not in contact with process***Plastic housing*

- Housing: PBT/PC
- Dummy cover: PBT/PC
- Cover with sight glass: PBT/PC and PC
- Cover seal: EPDM
- Potential equalization: 316L
- Seal under potential equalization: EPDM
- Plug: PBT-GF30-FR
- M20 cable gland: PA
- Seal on plug and cable gland: EPDM
- Threaded adapter as replacement for cable glands: PA66-GF30
- Nameplate: plastic foil
- TAG plate: plastic foil, metal or provided by customer

*Aluminum housing, coated*

- Housing: EN AC-43400 aluminum
- Housing coating, cover: Polyester
- Dummy cover: EN AC-43400 aluminum
- EN AC-43400 aluminum cover with Lexan 943A PC sight glass  
EN AC-43400 aluminum cover with borosilicate sight glass; can be ordered as an accessory optionally  
For Ex d, dust Ex applications, the sight glass is always made from borosilicate.
- Cover seal materials: HNBR
- Cover seal materials: FVMQ (only for low temperature version)
- Nameplate: plastic foil
- TAG plate: plastic foil, stainless steel or provided by customer
- M20 cable glands: select material (stainless steel, nickel-plated brass, polyamide)

*Stainless steel housing, 316L*


- Housing: stainless steel 316L (1.4409)
- Dummy cover: stainless steel 316L (1.4409)
- 316L (1.4409) stainless steel cover with borosilicate window
- Cover seal materials: FVMQ (only for low temperature version)
- Cover seal materials: HNBR
- Nameplate: stainless steel housing, labeled directly
- TAG plate: plastic foil, stainless steel or provided by the customer
- M20 cable glands: select material (stainless steel, nickel-plated brass, polyamide)

*Stainless steel housing, 316L hygiene*

- Housing: stainless steel 316L (1.4404)
- Dummy cover: stainless steel 316L (1.4404)
- 316L (1.4404) stainless steel cover with PC Lexan 943A window  
316L (1.4404) stainless steel cover with borosilicate window; can be optionally ordered as an enclosed accessory  
For Dust-Ex applications, the window is always made from borosilicate.
- Cover seal materials: EPDM
- Nameplate: stainless steel housing, labeled directly
- TAG plate: plastic foil, stainless steel or provided by the customer
- M20 cable glands: select material (stainless steel, nickel-plated brass, polyamide)

### Materials in contact with the medium

*Integrated antenna, PEEK, 20 mm / M24×1.5*




A0046101

51 Material; integrated antenna, PEEK, 20 mm / M24×1.5

- 1 Antenna: PEEK, seal material can be selected (order option)
- 2 Process connection: 316L / 1.4404
- 3 Housing adapter: 316L / 1.4404

*Antenna, cladded flush mount, 50 mm (2 in), slotted nut DIN11851*




A0046619

52 Material; antenna, cladded flush mount, 50 mm (2 in), slotted nut DIN11851

- 1 Antenna: PTFE, seal material PTFE cladding
- 2 DIN11851 slotted nut: 304L / 1.4307
- 3 Antenna adapter: 316L / 1.4404
- 4 Housing adapter: 316L / 1.4404

Antenna, cladded flush mount, 80 mm (3 in), slotted nut DIN11851




A0046620

53 Material; antenna, cladded flush mount, 80 mm (3 in), slotted nut DIN11851. Unit of measurement mm (in)

- 1 Antenna: PTFE, seal material PTFE cladding
- 2 DIN11851 slotted nut: 304L / 1.4307
- 3 Antenna adapter: 316L / 1.4404
- 4 Housing adapter: 316L / 1.4404

Antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp ISO2852




A0046607

54 Material; antenna, cladded flush mount, PTFE, 50 mm (2 in), with Tri-Clamp ISO2852. Unit of measurement mm (in)

- 1 Antenna: PTFE, seal material PTFE cladding
- 2 Antenna adapter: 316L / 1.4404
- 3 Housing adapter: 316L / 1.4404

Antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp ISO2852



A0046608

■ 55 Material; antenna, cladded flush mount, PTFE, 80 mm (3 in), with Tri-Clamp ISO2852

- 1 Antenna: PTFE, seal material PTFE cladding
- 2 Antenna adapter: 316L / 1.4404
- 3 Housing adapter: 316L / 1.4404

## Operability

### Operating concept

#### Operator-oriented menu structure for user-specific tasks

- Guidance
- Diagnostics
- Application
- System

#### Fast and safe commissioning

- Interactive wizard with graphical user interface for guided commissioning in FieldCare, DeviceCare or DTM, AMS and PDM-based third-party tools or SmartBlue
- Menu guidance with short explanations of the individual parameter functions
- Standardized operation at the device and in the operating tools

#### Integrated HistoROM data memory

- Adoption of data configuration when electronics modules are replaced
- Up to 100 event messages recorded in the device

#### Efficient diagnostic behavior increases measurement availability

- Remedial measures are integrated in plain text
- Diverse simulation options

#### Bluetooth (optionally integrated in local display)

- Quick and easy setup with SmartBlue app or PC with DeviceCare, version 1.07.05 and higher, or FieldXpert SMT70
- No additional tools or adapters required
- Encrypted single point-to-point data transmission (tested by Fraunhofer Institute) and password-protected communication via *Bluetooth®* wireless technology

### Languages


#### Operating languages

- **English** option (**English** option is set at the factory if no other language is ordered)
- Deutsch
- Français
- Español
- Italiano
- Nederlands
- Portuguesa
- Polski
- русский язык (Russian)

- Türkçe
- 中文 (Chinese)
- 日本語 (Japanese)
- 한국어 (Korean)
- čeština (Czech)
- Svenska

Local operation

Operating keys and DIP switches on the HART electronic insert



56 Operating keys and DIP switches on the HART electronic insert

- 1 Operating key for reset password (for Bluetooth login and Maintenance user role)
- 1+2 Operating keys for device reset (as-delivered state)
- 2 Operating key II (only for factory reset)
- 3 DIP switch for alarm current
- 4 DIP switch for locking and unlocking the device


**i** The setting of the DIP switches on the electronic insert has priority over the settings made via other operation methods (e.g. FieldCare/DeviceCare).

Local display

Device display (optional)

Functions:

- Display of measured values and fault and notice messages
- Background lighting, which switches from green to red in the event of an error
- The device display can be removed for easier operation



57 Graphic display with optical operating keys (1)



**Remote operation****Via HART protocol****Via service interface (CDI)****Operation via Bluetooth® wireless technology (optional)**

Prerequisite

- Measuring device with display including Bluetooth
- Smartphone or tablet with Endress+Hauser SmartBlue app or PC with DeviceCare from version 1.07.05 or FieldXpert SMT70

The connection has a range of up to 25 m (82 ft). The range can vary depending on environmental conditions such as attachments, walls or ceilings.



The operating keys on the display are locked as soon as the device is connected via Bluetooth.

**System integration****HART**

Version 7

**Supported operating tools**

Smartphone or tablet with Endress+Hauser SmartBlue app, DeviceCare from version 1.07.05, FieldCare, DTM, AMS and PDM

## Certificates and approvals

Current certificates and approvals for the product are available at [www.endress.com](http://www.endress.com) on the relevant product page:

1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Downloads**.

**CE mark**

The measuring system meets the legal requirements of the applicable EU directives. These are listed in the corresponding EU Declaration of Conformity together with the standards applied.

The manufacturer confirms successful testing of the device by affixing to it the CE mark.

**RoHS**

The measuring system meets the substance restrictions of the Directive on the Restriction of the Use of Certain Hazardous Substances 2011/65/EU (RoHS 2) and the Delegated Directive (EU) 2015/863 (RoHS 3).

**RCM marking**

The supplied product or measuring system meets the ACMA (Australian Communications and Media Authority) requirements for network integrity, interoperability, performance characteristics as well as health and safety regulations. Here, especially the regulatory arrangements for electromagnetic compatibility are met. The products bear the RCM marking on the nameplate.



A0029561

**Ex approvals**

Additional safety instructions must be followed for use in hazardous areas. Please refer to the separate "Safety Instructions" (XA) document included in the delivery. Reference to the applicable XA can be found on the nameplate.

**Explosion-protected smartphones and tablets**

If used in hazardous areas, mobile end devices with an Ex approval must be used.

<b>Functional safety</b>	Use for level monitoring (MIN, MAX, range) up to SIL 3 (homogeneous or diverse redundancy), independently evaluated by TÜV Rheinland in accordance with IEC 61508, refer to the "Functional Safety Manual" for information.
<b>Pressure equipment with permitted pressure ≤ 200 bar (2 900 psi)</b>	<p>Pressure instruments with a process connection that does not have a pressurized housing do not fall within the scope of the Pressure Equipment Directive, irrespective of the maximum allowable pressure.</p> <p><b>Reasons:</b></p> <p>According to Article 2, point 5 of EU Directive 2014/68/EU, pressure accessories are defined as "devices with an operational function and having pressure-bearing housings".</p> <p>If a pressure instrument does not have a pressure-bearing housing (no identifiable pressure chamber of its own), there is no pressure accessory present within the meaning of the Directive.</p>
<b>Radio approval</b>	Displays with Bluetooth LE have radio licenses according to CE and FCC. The relevant certification information and labels are provided on display.
<b>EN 302372 radio standard</b>	The devices comply with the TLPR (Tanks Level Probing Radar) radio standard EN 302372 and are permitted for use in closed vessels. Points a to f in Annex E of EN 302372 must be observed for the installation.
<b>FCC</b>	<p>This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.</p> <p>[Any] changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.</p> <p>The devices are compliant with the FCC Code of Federal Regulations, CFR 47, Part 15, Sections 15.205, 15.207, 15.209.</p>
<b>Industry Canada</b>	<p><b>Canada CNR-Gen Section 7.1.3</b></p> <p>This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions: (1) This device may not interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.</p> <p><i>Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes : (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.</i></p> <p>[Any] changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.</p> <ul style="list-style-type: none"> <li>■ The installation of the LPR/TLPR device shall be done by trained installers, in strict compliance with the manufacturer's instructions.</li> <li>■ The use of this device is on a "no-interference, no-protection" basis. That is, the user shall accept operations of high-powered radar in the same frequency band which may interfere with or damage this device. However, devices found to interfere with primary licensing operations will be required to be removed at the user's expense.</li> <li>■ This device shall be installed and operated in a completely enclosed container to prevent RF emissions, which can otherwise interfere with aeronautical navigation.</li> <li>■ The installer/user of this device shall ensure that it is at least 10 km from the Dominion Astrophysical Radio Observatory (DRAO) near Penticton, British Columbia. The coordinates of the DRAO are latitude 49°19'15" N and longitude 119°37'12" W. For devices not meeting this 10 km separation (e.g., those in the Okanagan Valley, British Columbia,) the installer/user must coordinate with, and obtain the written concurrence of, the Director of the DRAO before the equipment can be installed or operated. The Director of the DRAO may be contacted at 250-497-2300 (tel.) or 250-497-2355 (fax). (Alternatively, the Manager, Regulatory Standards Industry Canada, may be contacted.)</li> </ul>

**Other standards and guidelines**

- EN 60529  
Degrees of protection provided by enclosures (IP code)
- EN 61010-1  
Safety requirements for electrical equipment for measurement, control and laboratory use
- IEC/EN 61326  
Emission in accordance with Class A requirements A; Electromagnetic compatibility (EMC requirements)
- NAMUR NE 21  
Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment
- NAMUR NE 43  
Standardization of the signal level for the breakdown information of digital transmitters with analog output signal
- NAMUR NE 53  
Software of field devices and signal-processing devices with digital electronics
- NAMUR NE 107  
Status categorization in accordance with NE 107
- NAMUR NE 131  
Requirements for field devices for standard applications
- IEC 61508  
Functional safety of safety-related electric/electronic/programmable electronic systems

## Ordering information

Detailed ordering information is available from your nearest sales organization [www.addresses.endress.com](http://www.addresses.endress.com) or in the Product Configurator at [www.endress.com](http://www.endress.com):


1. Select the product using the filters and search field.
2. Open the product page.
3. Select **Configuration**.

**Product Configurator - the tool for individual product configuration**

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

**Calibration****Factory calibration certificate**

The calibration points are spread evenly over the measuring range (0 to 100 %). The Empty calibration **E** and Full calibration **F** must be specified to define the measuring range. If this information is missing, antenna-dependent default values are used instead.




A0032643

- R Reference point of measurement  
 A Minimum distance between reference point R and 100% mark  
 E Empty calibration  
 F Full calibration

**Measuring range restrictions**

The following restrictions must be considered when selecting **E** and **F**:

- Minimum distance between reference point **R** and **100%** mark  
 $A \geq 400 \text{ mm (16 in)}$
- Minimum span  
 $F \geq 45 \text{ mm (1.77 in)}$
- Maximum value for Empty calibration  
 $E \geq 450 \text{ mm (17.72 in)}$  (maximum 50 m (164 ft))
-  ■ Calibration takes place under reference conditions .
- The selected values for Empty calibration and Full calibration are only used to create the factory calibration certificate. Afterwards, the values are reset to the default values specific for the antenna. If values other than the default values are required, they must be ordered as a customized empty/full calibration.  
 Product Configurator → Optional → Service → **Customized empty/full calibration**

**Service**

The following services, among others, can be selected via the Product Configurator.

- Cleaned of oil+grease (wetted)
  - PWIS-free (paint-wetting impairment substances)
  - ANSI Safety Red coating, coated housing cover
  - Set damping
  - Set HART Burst Mode PV
  - Set max. alarm current
  - Bluetooth communication is disabled on delivery
  - Customized empty/full calibration
  - Product documentation on paper
- A printed (hard copy) version of test reports, declarations and inspection certificates can optionally be ordered via the **Service** feature, **Product documentation on paper** type. The documents can be selected via the **Test, certificate, declaration** feature are then provided with the device upon delivery.

**Test, certificate, declaration**

All test reports, declarations and inspection certificates are provided electronically in the *Device Viewer*:  
 Enter the serial number from the nameplate ([www.endress.com/deviceviewer](http://www.endress.com/deviceviewer))

**Identification****Measuring point (TAG)**

The device can be ordered with a tag name.

**Location of tag name**

In the additional specification, select:

- Stainless steel tag plate
- Paper adhesive label
- TAG provided by customer
- RFID TAG
- RFID TAG + stainless steel tag plate
- RFID TAG + paper adhesive label
- RFID TAG + TAG provided by customer
- IEC 61406 stainless steel TAG
- IEC 61406 stainless steel TAG + NFC TAG
- IEC 61406 stainless steel TAG, stainless steel TAG
- IEC 61406 stainless steel TAG + NFC, stainless steel TAG
- IEC 61406 stainless steel TAG, plate provided
- IEC 61406 stainless steel TAG + NFC, plate provided

**Definition of the tag name**

In the additional specification, specify:

3 lines with a maximum of 18 characters per line

The specified tag name appears on the selected plate and/or on the RFID tag.

**Presentation in the SmartBlue app**

The first 32 characters of the tag name

The tag name can always be changed specifically for the measuring point via Bluetooth.

**Display in electronic nameplate (ENP)**

The first 32 characters of the tag name



For further information, please refer to SD01502F, SD02796P

Available in the Download Area of the Endress+Hauser website ([www.endress.com/downloads](http://www.endress.com/downloads)).

## Application packages

---

**Heartbeat Technology**

The Heartbeat Verification + Monitoring application package offers diagnostic functionality through continuous self-monitoring, the transmission of additional measured variables to an external Condition Monitoring system and the in-situ verification of devices in the application.

The application package can be ordered together with the device or can be activated subsequently with an activation code. Detailed information on the order code is available via the Endress+Hauser website [www.endress.com](http://www.endress.com) or from your local Endress+Hauser Sales Center.

**Heartbeat Verification**




Heartbeat Verification is carried out on request and supplements self-monitoring, which is performed continuously, by carrying out further tests. During verification, the system checks whether the device components comply with the factory specifications. Both the sensor and the electronics modules are included in the tests.

Heartbeat Verification confirms the device function on request within the specified measuring tolerance with a total test coverage TTC (Total Test Coverage) in percent.

Heartbeat Verification meets the requirements for metrological traceability in accordance with ISO 9001 (ISO9001:2015 Section 7.1.5.2).

The result of the verification is either Passed or Failed. The verification data are saved in the device and optionally archived on a PC with the FieldCare asset management software or in the Netilion Library. Based on this data, a verification report is generated automatically to ensure that traceable documentation of the verification results is available.

**Heartbeat Monitoring**

**Loop diagnostics** wizard (→  61), **Foam detection** wizard (→  61) and **Build-up detection** wizard (→  62) are available. In addition, other monitoring parameters can be output for use in predictive maintenance or application optimization.

*"Loop diagnostics" wizard*

Using this wizard, changes in the current-voltage loop characteristics (baseline) can be used to detect unwanted installation anomalies such as creep currents caused by terminal corrosion or a deteriorating power supply that can lead to an incorrect 4-20 mA measured value.

*Areas of application*

- Detection of changes in the measuring circuit resistance due to anomalies  
Examples: Contact resistance or leakage currents in wiring, terminals or grounding due to corrosion and/or moisture
- Detection of faulty power supply

*"Foam detection" wizard*

This wizard configures the automatic foam detection.

Foam detection can be linked to an output variable or status information e.g. to control a sprinkler used to dissolve the foam. It is also possible to monitor the foam increase in a so called foam index. The foam index can also be linked to an output variable and can be shown on the display.

*Preparation:*

The Foam monitoring initialization should only be done without or less foam.

*Areas of application*

- Measurement in liquids
- Reliable detection of foam on the medium

*"Build-up detection" wizard*

This wizard configures the build-up detection.

Basic idea:

The build-up detection can, for example, be linked to a compressed-air system to clean the antenna. With the build-up monitoring the maintenance cycles can be optimized.

Preparation:

The build-up monitoring initialization should only be done without or less build-up.

*Areas of application*

- Measurement in liquids and solids
- Reliable detection of buildup on the antenna

**Detailed description**

 Special Documentation SD02953F


## Accessories

**Weather protection cover  
316L**

The weather protection cover can be ordered together with the device via the "Accessory enclosed" product structure.

It is used to protect against direct sunlight, precipitation and ice.

Weather protection cover 316L is suitable for the dual compartment housing made of aluminum or 316L. The delivery includes the holder for direct mounting on the housing.



 58 Dimensions. Unit of measurement mm (in)

**Material**

- Weather protection cover: 316L
- Clamping screw: A4
- Holder: 316L

**Order number for accessories:**


71438303

**Plastic weather protection  
cover**

The weather protection cover can be ordered together with the device via the "Accessory enclosed" product structure.

It is used to protect against direct sunlight, precipitation and ice.

The plastic weather protection cover is suitable for the single compartment housing made of aluminum. The delivery includes the holder for direct mounting on the housing.



A0038280

59 Dimensions. Unit of measurement mm (in)


### Material

Plastic

### Order number for accessories:

71438291

## M12 socket




A0051231

60 M12 socket, straight

### M12 socket, straight

- Material:  
Body: PBT; union nut: nickel-plated die-cast zinc; seal: NBR
- Degree of protection (fully locked): IP67
- Pg coupling: Pg7
- Order number: 52006263




A0051232

61 M12 socket, angled

### M12 socket, angled

- Material:  
Body: PBT; union nut: nickel-plated die-cast zinc; seal: NBR
- Degree of protection (fully locked): IP67
- Pg coupling: Pg7
- Order number: 71114212



A0051233

62 M12 socket, angled, cable


#### M12 socket, angled, 5 m (16 ft) cable

- M12 socket material:
  - Body: TPU
  - Union nut: nickel-plated die-cast zinc
- Cable material: PVC
- Cable Li Y YM 4×0.34 mm<sup>2</sup> (20 AWG)
- Cable colors
  - 1 = BN = brown
  - 2 = WH = white
  - 3 = BU = blue
  - 4 = BK = black
- Order number: 52010285

#### Remote display FHX50B

The remote display is ordered via the Product Configurator.

If the remote display is to be used, the device version **Prepared for display FHX50B** must be ordered.



A0046692

- A Plastic single compartment housing, remote display
- B Aluminum single compartment housing, remote display
- C Single compartment housing, 316L hygiene, remote display
- D Device side, plastic single compartment housing prepared for display FHX50B
- E Device side, aluminum single compartment housing prepared for display FHX50B
- F Device side, dual compartment housing, L-form, prepared for display FHX50B
- G Device side, single compartment housing, 316L hygiene, prepared for display FHX50B



**Material of single compartment housing, remote display**

- Aluminum
- Plastic

**Degree of protection:**

- IP68 / NEMA 6P
- IP66 / NEMA 4x

**Connecting cable:**

- Connecting cable (option) up to 30 m (98 ft)
- Customer-supplied standard cable up to 60 m (197 ft)  
Recommendation: EtherLine®-P CAT.5e from LAPP.

**Specification of customer-supplied connecting cable**


Push-in CAGE CLAMP®, connection technology, push actuation

- Conductor cross-section:
  - Solid conductor 0.2 to 0.75 mm<sup>2</sup> (24 to 18 AWG)
  - Fine-stranded conductor 0.2 to 0.75 mm<sup>2</sup> (24 to 18 AWG)
  - Fine-stranded conductor; with insulated ferrule 0.25 to 0.34 mm<sup>2</sup>
  - Fine-stranded conductor; without insulated ferrule 0.25 to 0.34 mm<sup>2</sup>
- Stripping length 7 to 9 mm (0.28 to 0.35 in)
- Outer diameter: 6 to 10 mm (0.24 to 0.4 in)
- Maximum cable length: 60 m (197 ft)


**Ambient temperature:**

- -40 to +80 °C (-40 to +176 °F)
- Option: -50 to +80 °C (-58 to +176 °F)

<b>Gas-tight feedthrough</b>	Chemically inert glass feedthrough, which prevents gases from entering the electronics housing. Can optionally be ordered as "Accessory mounted" via the product structure.
------------------------------	--

<b>Process adapter M24</b>	 For details, refer to TI00426F/00/EN "Weld-in adapters, process adapters and flanges".
----------------------------	--

<b>Commubox FXA195 HART</b>	For intrinsically safe HART communication with FieldCare via the USB interface
-----------------------------	--

 For details, see "Technical Information" TI00404F

<b>HART Loop Converter HMX50</b>	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.
--------------------------------------	---

**Order number:**

71063562

 For details, see "Technical Information" TI00429F and Operating Instructions BA00371F

<b>FieldPort SWA50</b>	Intelligent Bluetooth® and/or WirelessHART adapter for all HART field devices
------------------------	---






 For details, see "Technical Information" TI01468S

<b>Wireless HART adapter SWA70</b>	The WirelessHART adapter is used for the wireless connection of field devices. It can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks.
--	--


 For details, see Operating Instructions BA00061S

<b>Fieldgate FXA42</b>	Fieldgates enable communication between connected 4 to 20 mA, Modbus RS485 and Modbus TCP devices and SupplyCare Hosting or SupplyCare Enterprise. The signals are transmitted either via Ethernet TCP/IP, WLAN or mobile communications (UMTS). Advanced automation capabilities are available, such as an integrated Web-PLC, OpenVPN and other functions.
------------------------	--


 For details, see "Technical Information" TI01297S and Operating Instructions BA01778S.

<b>Field Xpert SMT70</b>	Universal, high-performance tablet PC for device configuration in Ex Zone 2 and non-Ex areas  For details, see "Technical Information" TI01342S
<b>DeviceCare SFE100</b>	Configuration tool for HART, PROFIBUS and FOUNDATION Fieldbus field devices  Technical Information TI01134S
<b>FieldCare SFE500</b>	FDT-based plant asset management tool It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.  Technical Information TI00028S
<b>Memograph M</b>	The Memograph M graphic data manager provides information on all the relevant process variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on an SD card or USB stick.  Technical Information TI00133R and Operating Instructions BA00247R
<b>RN42</b>	Single-channel active barrier with wide-range power supply for safe electrical isolation of 4 to 20 mA standard signal circuits, HART transparent.  Technical Information TI01584K and Operating Instructions BA02090K

## Documentation

-  For an overview of the scope of the associated Technical Documentation, refer to the following:
- *Device Viewer* ([www.endress.com/deviceviewer](http://www.endress.com/deviceviewer)): Enter the serial number from the nameplate
  - *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

<b>Document function</b>	The following documentation may be available depending on the version ordered:
Document type	Purpose and content of the document
Technical Information (TI)	<b>Planning aid for your device</b> The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.
Brief Operating Instructions (KA)	<b>Guide that takes you quickly to the 1st measured value</b> The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning.
Operating Instructions (BA)	<b>Your reference document</b> The Operating Instructions contain all the information that is required in the various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal.
Description of Device Parameters (GP)	<b>Reference for your parameters</b> The document provides a detailed explanation of each individual parameter. The description is aimed at those who work with the device over the entire life cycle and perform specific configurations.

Document type	Purpose and content of the document
Safety Instructions (XA)	Depending on the approval, safety instructions for electrical equipment in hazardous areas are also supplied with the device. The Safety Instructions are an integral part of the Operating Instructions.  Information on the Safety Instructions (XA) relevant to the device is provided on the nameplate.
Supplementary device-dependent documentation (SD/FY)	Always comply strictly with the instructions in the relevant supplementary documentation. The supplementary documentation is an integral part of the device documentation.

## Registered trademarks

### **HART®**

Registered trademark of the FieldComm Group, Austin, Texas, USA

### **Bluetooth®**

The *Bluetooth*® word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Endress+Hauser is under license. Other trademarks and trade names are those of their respective owners.

### **Apple®**

Apple, the Apple logo, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc.

### **Android®**

Android, Google Play and the Google Play logo are trademarks of Google Inc.

### **KALREZ®, VITON®**

Registered trademarks of DuPont Performance Elastomers L.L.C., Wilmington, DE USA

### **TRI-CLAMP®**

Registered trademark of Ladish & Co., Inc., Kenosha, USA



[www.addresses.endress.com](http://www.addresses.endress.com)

---