Technical Information **Proline Promag H 300**

Electromagnetic flowmeter



Specialist for hygienic applications with a compact, easily accessible transmitter

Application

The bidirectional measuring principle is virtually independent of pressure, density, temperature and viscosity
For applications with sanitary requirements

Device properties

- Liner made of PFA
- Sensor housing made of stainless steel (3-A, EHEDG)
- Wetted materials CIP-/SIP-cleanable
- Compact hygienic dual-compartment housing with IP69 and up to 3 I/Os
- Backlit display with touch control and WLAN access
- Remote display available

Your benefits

- Flexible installation concept numerous hygienic process connections
- Energy-saving flow measurement no pressure loss due to cross section constriction
- Maintenance-free no moving parts
- Full access to process and diagnostic information numerous, freely combinable I/Os and Ethernet
- Reduced complexity and variety freely configurable I/O functionality
- Integrated verification Heartbeat Technology



Table of contents

| About this document | |
|---------------------------------------|-----------------|
| Symbols | . 4 |
| Providence and a second action | - |
| Function and system design | |
| Measuring principle | |
| Measuring system | |
| Equipment architecture | |
| Reliability | / |
| Input | . 9 |
| Measured variable | |
| Measuring range | |
| Operable flow range | |
| Input signal | |
| Output | 13 |
| | 13 |
| Output and input variants | 13 |
| Output signal Signal on alarm | 15 20 |
| 5 | 20 |
| Load | 23 23 |
| Low flow cut off | 25 |
| Galvanic isolation | 25 |
| Protocol-specific data | 25 |
| | ر ۲ |
| Power supply | 32 |
| Terminal assignment | 32 |
| Available device plugs | 33 |
| Supply voltage | 34 |
| Power consumption | 34 |
| Current consumption | 34 |
| Power supply failure | 34 |
| Overcurrent protection element | 34 |
| Electrical connection | 35 |
| Terminals | 45 |
| Cable entries | 46 |
| Pin assignment, device plug | 46 |
| Cable specification | 47 |
| Overvoltage protection | 50 |
| Performance characteristics | 50 |
| Reference operating conditions | 50 |
| Maximum measurement error | 51 |
| Repeatability | 52 |
| Temperature measurement response time | 52 |
| Influence of ambient temperature | 53 |
| Mounting | 53 |
| Mounting | رر 53 |
| Mounting location | 55 |
| Inlet and outlet runs | 50 56 |
| Adapters | 50 |
| Special mounting instructions | 57 |
| - • • | |
| Environment | 58 |
| Ambient temperature range | 58 |
| Storage temperature | 58 |

| AtmosphereRelative humidityOperating heightDegree of protectionVibration-resistance and shock-resistanceInternal cleaningMechanical loadElectromagnetic compatibility (EMC) | 58 58 |
|--|--|
| Process | 59 59 65 65 65 65 |
| Mechanical construction | 98 99 |
| Operability | 103 103 103 104 110 111 112 113 |
| Certificates and approvals . CE mark . UKCA marking . RCM marking . Ex approval . Sanitary compatibility . Pharmaceutical compatibility . EtherNet/IP certification . Certification PROFINET . PROFINET with Ethernet-APL certification . Radio approval . | 115 115 115 115 116 116 116 117 117 117 118 118 118 |

| Ordering information | 119 |
|---|--|
| Application packagesDiagnostic functionalityHeartbeat TechnologyCleaningOPC-UA Server | 119 120 120 120 120 |
| Accessories | 120 121 122 123 123 |
| Supplementary documentation Standard documentation Supplementary device-dependent documentation | 123 123 124 |
| Registered trademarks | 125 |

About this document

Symbols

Electrical symbols

| Symbol | Meaning |
|----------|--|
| | Direct current |
| \sim | Alternating current |
| \sim | Direct current and alternating current |
| <u> </u> | Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system. |
| | Potential equalization connection (PE: protective earth) Ground terminals that must be connected to ground prior to establishing any other connections. |
| | The ground terminals are located on the interior and exterior of the device:Interior ground terminal: potential equalization is connected to the supply network.Exterior ground terminal: device is connected to the plant grounding system. |

Communication-specific symbols

| Symbol | Meaning |
|--------|--|
| ((:- | Wireless Local Area Network (WLAN) Communication via a wireless, local network. |

Symbols for certain types of information

| Symbol | Meaning |
|---------|--|
| | Permitted Procedures, processes or actions that are permitted. |
| | Preferred Procedures, processes or actions that are preferred. |
| × | Forbidden Procedures, processes or actions that are forbidden. |
| i | Tip Indicates additional information. |
| <u></u> | Reference to documentation |
| | Reference to page |
| | Reference to graphic |
| | Visual inspection |

Symbols in graphics


| Symbol | Meaning |
|----------------|-----------------|
| 1, 2, 3, | Item numbers |
| 1., 2., 3., | Series of steps |
| A, B, C, | Views |
| A-A, B-B, C-C, | Sections |

| Symbol | Meaning |
|------------|--------------------------------|
| <u></u> EX | Hazardous area |
| X | Safe area (non-hazardous area) |
| ≈ → | Flow direction |

Function and system design

Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



- Ue Induced voltage
- *B Magnetic induction (magnetic field)*
- L Electrode spacing
- I Current
- v Flow velocity

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced (U_e) is proportional to the flow velocity (v) and is supplied to the amplifier by means of two measuring electrodes. The flow volume (Q) is calculated via the pipe cross-section (A). The magnetic field is created through a switched direct current of alternating polarity.

Formulae for calculation

- Induced voltage $U_e = B \cdot L \cdot v$
- Volume flow $Q = A \cdot v$

Measuring system


The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.


Transmitter

| Proline 300 | Device versions and materials: Transmitter housing Aluminum, coated: aluminum, AlSi10Mg, coated Stainless, hygienic: stainless steel, 1.4404 Material of window in transmitter housing: Aluminum, coated: glass Stainless, hygienic: polycarbonate |
|-------------|---|
| A0026708 | Configuration: External operation via 4-line, illuminated graphic local display (LCD) with touch control and guided menus ("Make-it-run" wizards) for application-specific commissioning. Via service interface or WLAN interface: Operating tools (e.g. FieldCare, DeviceCare) Web server (access via Web browser, e.g. Microsoft Internet Explorer, Microsoft Edge) |

Sensor



Equipment architecture



• 1 Possibilities for integrating measuring devices into a system

- 1 Control system (e.g. PLC)
- 2 Connecting cable (0/4 to 20 mA HART etc.)
- 3 Fieldbus
- 4 Coupler
- 5 Non-hazardous area
- 6 Hazardous area: Zone 2; Class I, Division 2 7
- Hazardous area: Zone 1; Class I, Division 1

Reliability

IT security

Our warranty is valid only if the product is installed and used as described in the Operating Instructions. The product is equipped with security mechanisms to protect it against any inadvertent changes to the settings.

IT security measures, which provide additional protection for the product and associated data transfer, must be implemented by the operators themselves in line with their security standards.

Device-specific IT security

The device offers a range of specific functions to support protective measures on the operator's side. These functions can be configured by the user and guarantee greater in-operation safety if used correctly. The following list provides an overview of the most important functions:

| Function/interface | Factory setting | Recommendation |
|--|------------------------|---|
| Write protection via hardware write protection switch $\rightarrow \textcircled{B} 8$ | Not enabled | On an individual basis following risk assessment |
| Access code (also applies to web server login or FieldCare connection) $\rightarrow \textcircled{B} 8$ | Not enabled (0000) | Assign a customized access code during commissioning |
| WLAN (order option in display module) | Enabled | On an individual basis following risk assessment |
| WLAN security mode | Enabled (WPA2- PSK) | Do not change |
| WLAN passphrase (Password) $\rightarrow \textcircled{B} 8$ | Serial number | Assign an individual WLAN passphrase during commissioning |
| WLAN mode | Access point | On an individual basis following risk assessment |
| Web server $\rightarrow \blacksquare 8$ | Enabled | On an individual basis following risk assessment |
| Service interface CDI-RJ45 → 🗎 9 | - | On an individual basis following risk assessment |

Protecting access via hardware write protection

Write access to the parameters of the device via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare) can be disabled via a write protection switch (DIP switch on the main electronics module). When hardware write protection is enabled, only read access to the parameters is possible.

Hardware write protection is disabled when the device is delivered.

Protecting access via a password

Different passwords are available to protect write access to the device parameters or access to the device via the WLAN interface.

User-specific access code

Protect write access to the device parameters via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare). Access authorization is clearly regulated through the use of a user-specific access code.

WLAN passphrase

The network key protects a connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface which can be ordered as an option.

Infrastructure mode

When the device is operated in infrastructure mode, the WLAN passphrase corresponds to the WLAN passphrase configured on the operator side.

User-specific access code

Write access to the device parameters via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare) can be protected by the modifiable, user-specific access code.

WLAN passphrase: Operation as WLAN access point

A connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface, which can be ordered as an optional extra, is protected by the network key. The WLAN authentication of the network key complies with the IEEE 802.11 standard.

When the device is delivered, the network key is pre-defined depending on the device. It can be changed via the **WLAN settings** submenu in the **WLAN passphrase** parameter.

Infrastructure mode

A connection between the device and WLAN access point is protected by means of an SSID and passphrase on the system side. Please contact the relevant system administrator for access.

General notes on the use of passwords


- The access code and network key supplied with the device should be changed during commissioning for safety reasons.
- Follow the general rules for generating a secure password when defining and managing the access code and network key.
- The user is responsible for the management and careful handling of the access code and network key.

Access via web server

The device can be operated and configured via a web browser with the integrated web server. The connection is established via the service interface (CDI-RJ45) or the WLAN interface. For device versions with the EtherNet/IP and PROFINET communication protocols, the connection can also be established via the terminal connection for signal transmission with EtherNet/IP, PROFINET (RJ45 plug) or PROFINET with Ethernet-APL (two-wire).

The web server is enabled when the device is delivered. The web server can be disabled via the **Web** server functionality parameter if necessary (e.g., after commissioning).

The device and status information can be hidden on the login page. This prevents unauthorized access to the information.



"Description of device parameters" document .

Access via OPC-UA

The "OPC UA Server" application package is available in the device version with the HART communication protocol $\rightarrow \cong 120$.

The device can communicate with OPC UA clients using the "OPC UA Server" application package.

The OPC UA server integrated in the device can be accessed via the WLAN access point using the WLAN interface - which can be ordered as an optional extra - or the service interface (CDI- RJ45) via Ethernet network. Access rights and authorization as per separate configuration.


The following Security Modes are supported as per the OPC UA Specification (IEC 62541):

- None
- Basic128Rsa15 signed
- Basic128Rsa15 signed and encrypted

Access via service interface (CDI-RJ45)

The device can be connected to a network via the service interface (CDI-RJ45). Device-specific functions guarantee the secure operation of the device in a network.

The use of relevant industrial standards and guidelines that have been defined by national and international safety committees, such as IEC/ISA62443 or the IEEE, is recommended. This includes organizational security measures such as the assignment of access authorization as well as technical measures such as network segmentation.



Order code for "Approval transmitter + sensor", options (Ex de): BA, BB, C1, C2, GA, GB, MA, MB, NA, NB BB, C2, GB, MB, NB



The device can be integrated into a ring topology. The device is integrated via the terminal connection for signal transmission (output 1) and the connection to the service interface (CDI-RJ45) $\rightarrow \cong 110$.

Input

| Measured variable | Direct measured variables | | | |
|-------------------|---|--|--|--|
| | Volume flow (proportional to induced voltage) Temperature ¹⁾ Electrical conductivity | | | |
| | Calculated measured variables | | | |
| | Mass flow Corrected volume flow Corrected electrical conductivity¹⁾ | | | |
| Measuring range | Typically $v = 0.01$ to 10 m/s (0.03 to 33 ft/s) with the specified accuracy | | | |
| | Flow characteristic values in SI units: DN 2 to 125 ($\frac{1}{12}$ to 5") | | | |

| Nominal | diameter | Recommended flow | Factory settings | | |
|---------|------------------------------|---|------------------|--------------------|------------------------------------|
| | | min./max. full scale value (v ~ 0.3/10 m/s) | current output | | Low flow cut off (v ~ 0.04 m/s) |
| [mm] | [in] | [dm³/min] | [dm³/min] | [dm ³] | [dm ³ /min] |
| 2 | 1/12 | 0.06 to 1.8 | 0.5 | 0.005 | 0.01 |
| 4 | 5/32 | 0.25 to 7 | 2 | 0.025 | 0.05 |
| 8 | ⁵ / ₁₆ | 1 to 30 | 8 | 0.1 | 0.1 |

¹⁾ Available only for nominal diameters DN 15 to 150 (½ to 6") and with the order code for "Sensor option", option CI "Medium temperature measurement".

| Nominal | diameter | Recommended flow | Factory settings | | | | | |
|------------------|----------|---|--------------------------------------|--------------------|------------------------------------|--|--|--|
| | | min./max. full scale value (v ~ 0.3/10 m/s) | ale value current output Pulse value | | Low flow cut off (v ~ 0.04 m/s) | | | |
| [mm] | [in] | [dm³/min] | [dm³/min] | [dm ³] | [dm ³ /min] | | | |
| 15 | 1/2 | 4 to 100 | 25 | 0.2 | 0.5 | | | |
| 25 ¹⁾ | 1 | 9 to 300 | 75 | 0.5 | 1 | | | |
| 40 | 1 1/2 | 25 to 700 | 200 | 1.5 | 3 | | | |
| 50 | 2 | 35 to 1 100 | 300 | 2.5 | 5 | | | |
| 65 | - | 60 to 2 000 | 500 | 5 | 8 | | | |
| 80 | 3 | 90 to 3 000 | 750 | 5 | 12 | | | |
| 100 | 4 | 145 to 4700 | 1200 | 10 | 20 | | | |
| 125 | 5 | 220 to 7 500 | 1850 | 15 | 30 | | | |

1) The values apply for the product version: 5HxB26

Flow characteristic values in SI units: DN 150 (6")


| Nominal diameter Recommended flow Factory settings | | | | | | |
|--|------|---|---|------------------------------|------------------------------------|--|
| | | min./max. full scale value (v ~ 0.3/10 m/s) | Full scale value current output (v ~ 2.5 m/s) | Pulse value (~ 2 pulse/s) | Low flow cut off (v ~ 0.04 m/s) | |
| [mm] | [in] | [m³/h] | [m³/h] | [m ³] | [m³/h] | |
| 150 | 6 | 20 to 600 | 150 | 0.03 | 2.5 | |

Flow characteristic values in US units: $^1\!\!\prime_{12}$ - 6" (DN 2 - 150)

| Nominal diameter Recommended flow Factory settings | | | | | | |
|--|------|---|---|------------------------------|--|--|
| | | min./max. full scale value (v ~ 0.3/10 m/s) | Full scale value current output (v ~ 2.5 m/s) | Pulse value (~ 2 pulse/s) | Low flow cut off (v ~ 0.04 m/s) | |
| [in] | [mm] | [gal/min] | [gal/min] | [gal] | [gal/ min] | |
| 1/12 | 2 | 0.015 to 0.5 | 0.1 | 0.001 | 0.002 | |
| 1/32 | 4 | 0.07 to 2 | 0.5 | 0.005 | 0.008 | |
| ⁵ / ₁₆ | 8 | 0.25 to 8 | 2 | 0.02 | 0.025 | |
| 1/2 | 15 | 1 to 27 | 6 | 0.05 | 0.1 | |
| 1 ¹⁾ | 25 | 2.5 to 80 | 18 | 0.2 | 0.25 | |
| 1 1/2 | 40 | 7 to 190 | 50 | 0.5 | 0.75 | |
| 2 | 50 | 10 to 300 | 75 | 0.5 | 1.25 | |
| 3 | 80 | 24 to 800 | 200 | 2 | 2.5 | |
| 4 | 100 | 40 to 1250 | 300 | 2 | 4 | |
| 5 | 125 | 60 to 1950 | 450 | 5 | 7 | |
| 6 | 150 | 90 to 2 650 | 600 | 5 | 12 | |

1) The values apply for the product version: 5HxB26

Recommended measuring range





H

For custody transfer, the applicable approval determines the permitted measuring range, the pulse value and the low flow cut off.

Operable flow range

Over 1000 : 1

For custody transfer, the operable flow range is 100 : 1 to 630 : 1, depending on the nominal diameter. Further details are specified by the applicable approval.

Input signal

Output and input variants

→ 🗎 13

External measured values

To increase the measurement accuracy of certain measured variables or to calculate the mass flow, the automation system can continuously write different measured values to the measuring instrument:

- Medium temperature enables temperature-compensated conductivity measurement (e.g. iTEMP)
- Reference density for calculating the mass flow

Yarious pressure and temperature measuring devices can be ordered from Endress+Hauser: see "Accessories" section →
123

It is recommended to read in external measured values to calculate the corrected volume flow.

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Current input

The measured values are written from the automation system to the measuring device via the current input $\rightarrow \cong 11$.

Digital communication

The measured values can be written by the automation system via:

- FOUNDATION Fieldbus
- PROFIBUS DP
- PROFIBUS PA
- Modbus RS485
- Modbus TCP over Ethernet-APL
- Ethernet/IP
- PROFINET
- PROFINET over Ethernet-APL

Current input 0/4 to 20 mA

| Current input | 0/4 to 20 mA (active/passive) | | | | |
|--------------------------|---|--|--|--|--|
| Current span | 4 to 20 mA (active) 0/4 to 20 mA (passive) | | | | |
| Resolution | 1 μΑ | | | | |
| Voltage drop | Typically: 0.6 to 2 V for 3.6 to 22 mA (passive) | | | | |
| Maximum input voltage | ≤ 30 V (passive) | | | | |
| Open-circuit voltage | < 28.8 V (active) | | | | |
| Possible input variables | TemperatureDensity | | | | |

Status input

| Maximum input values | DC -3 to 30 V If status input is active (ON): R_i >3 kΩ |
|----------------------|--|
| Response time | Configurable: 5 to 200 ms |
| Input signal level | Low signal: DC -3 to +5 V High signal: DC 12 to 30 V |
| Assignable functions | Off Reset the individual totalizers separately Reset all totalizers Flow override |

Output

| Output and input variants | Depending on the option selected for output/input 1, different options are available for the other outputs and inputs. Only one option can be selected for each output/input 1 to 3. The following tables must be read vertically (\downarrow). |
|---------------------------|---|
| | Example: If the option BA "4–20 mA HART" was selected for output/input 1, one of the options A, B, D, E, F, H, I or J is available for output 2 and one of the options A, B, D, E, F, H, I or J is available for output 3. |
| | Output/input 1 and options for output/input 2 |

ut/input 1 and options for output/input 2



Options for output/input $3 \rightarrow \cong 14$

| Order code for "Output; input 1" (020) → | Possible options | | | | | | | | | | | | |
|--|------------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|
| Current output 4 to 20 mA HART | BA | | | | | | | | | | | | |
| Current output 4 to 20 mA HART Ex i passive | \downarrow | CA | | | | | | | | | | | |
| Current output 4 to 20 mA HART Ex i active | | \downarrow | сс | | | | | | | | | | |
| FOUNDATION Fieldbus | | | \downarrow | SA | | | | | | | | | |
| FOUNDATION Fieldbus Ex i | | | | \downarrow | TA | | | | | | | | |
| PROFIBUS DP | | | | | \downarrow | LA | | | | | | | |
| PROFIBUS PA | | | | | | \downarrow | GA | | | | | | |
| PROFIBUS PA Ex i | | | | | | | \downarrow | HA | | | | | |
| Modbus RS485 | | | | | | | | \downarrow | MA | | | | |
| EtherNet/IP 2-port switch integrated | | | | | | | | | \downarrow | NA | | | |
| PROFINET 2-port switch integrated | | | | | | | | | | \downarrow | RA | | |
| PROFINET over Ethernet-APL | | | | | | | | | | | \downarrow | RB | |
| PROFINET over Ethernet-APL Ex i | | | | | | | | | | | | \downarrow | RC |
| Order code for "Output; input 2" (021) → | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow | \downarrow |
| Not used | A | A | Α | A | A | A | A | A | A | Α | Α | Α | Α |
| Current output 4 to 20 mA | В | | | В | | В | В | | В | В | В | В | |
| Current output 4 to 20 mA Ex i passive | | С | С | | С | | | С | | | | | С |
| User-configurable input/output ¹⁾ | D | | | D | | D | D | | D | D | D | D | |
| Pulse/frequency/switch output | E | | | E | | E | Е | | E | Е | Е | Е | |
| Double pulse output ²⁾ | F | | | | | | | | F | | | | |
| Pulse/frequency/switch output Ex i passive | | G | G | | G | | | G | | | | | G |
| Relay output | н | | | н | | н | н | | н | н | н | н | |
| Current input 0/4 to 20 mA | I | | | I | | I | I | | I | Ι | Ι | Ι | |
| Status input | J | | | J | | J | J | | J | J | J | J | |

1)

A specific input or output can be assigned $\rightarrow \bigoplus$ 20 to a user-configurable input/output. If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for selection for output/input 3 2) (022).

Output/input 1 and options for output/input 3

Options for output/input $2 \rightarrow \square 13$

| Order code for "Output; input 1" (020) → | | | | | : | Possi | ble o | ption | S | | | | |
|--|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|
| Current output 4 to 20 mA HART | BA | | | | | | | | | | | | |
| Current output 4 to 20 mA HART Ex i passive | \downarrow | CA | | | | | | | | | | | |
| Current output 4 to 20 mA HART Ex i active | | \downarrow | CC | | | | | | | | | | |
| FOUNDATION Fieldbus | | | \downarrow | SA | | | | | | | | | |
| FOUNDATION Fieldbus Ex i | | | | \downarrow | TA | | | | | | | | |
| PROFIBUS DP | | | | | \downarrow | LA | | | | | | | |
| PROFIBUS PA | | | | | | \downarrow | GA | | | | | | |
| PROFIBUS PA Ex i | | | | | | | \downarrow | HA | | | | | |
| Modbus RS485 | | | | | | | | \downarrow | MA | | | | |
| EtherNet/IP 2-port switch integrated | | | | | | | | | \downarrow | NA | | | |
| PROFINET 2-port switch integrated | | | | | | | | | | \downarrow | RA | | |
| PROFINET over Ethernet-APL/SPE, 10 Mbit/s, 2-wire | | | | | | | | | | | \downarrow | RB | |
| PROFINET over Ethernet-APL Ex i, 10 Mbit/s, 2-wire | | | | | | | | | | | | \downarrow | RC |
| Order code for "Output; input 3" (022) → | \downarrow |
| Not used | A | Α | Α | A | Α | A | Α | Α | A | Α | Α | Α | Α |
| Current output 4 to 20 mA | В | | | | | В | | | В | В | В | В | |
| Current output 4 to 20 mA Ex i passive | | С | С | | | | | | | | | | |
| User-configurable input/output | D | | | | | D | | | D | D | D | D | |
| Pulse/frequency/switch output | E | | | | | Е | | | E | E | Е | Е | |
| Double pulse output (slave) ¹⁾ | F | | | | | | | | F | | | | |
| Pulse/frequency/switch output Ex i passive | | G | G | | | | | | | | | | |
| Relay output | н | | | | | н | | | н | н | н | н | |
| Current input 0/4 to 20 mA | I | | | | | I | | | I | I | I | I | |
| Status input | J | | | | | J | | | J | J | J | J | |

1) If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for output/input 3 (022).

Output signal

Current output 4 to 20 mA HART

| Order code | "Output; input 1" (20): Option BA: current output 4 to 20 mA HART |
|----------------------------------|--|
| Signal mode | Can be set to: • Active • Passive |
| Current range | Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current |
| Open-circuit voltage | DC 28.8 V (active) |
| Maximum input voltage | DC 30 V (passive) |
| Load | 250 to 700 Ω |
| Resolution | 0.38 μΑ |
| Damping | Configurable: 0 to 999.9 s |
| Assignable measured variables | Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature |

Current output 4 to 20 mA HART Ex i

| Order code | "Output; input 1" (20) choose from: Option CA: current output 4 to 20 mA HART Ex i passive Option CC: current output 4 to 20 mA HART Ex i active |
|----------------------------------|--|
| Signal mode | Depends on the selected order version. |
| Current range | Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current |
| Open-circuit voltage | DC 21.8 V (active) |
| Maximum input voltage | DC 30 V (passive) |
| Load | 250 to 400 Ω (active) 250 to 700 Ω (passive) |
| Resolution | 0.38 μΑ |
| Damping | Configurable: 0 to 999.9 s |
| Assignable measured variables | Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature |

FOUNDATION Fieldbus

| FOUNDATION Fieldbus | H1, IEC 61158-2, galvanically isolated |
|--------------------------|---|
| Data transfer | 31.25 kbit/s |
| Current consumption | 10 mA |
| Permitted supply voltage | 9 to 32 V |
| Bus connection | With integrated reverse polarity protection |

PROFIBUS DP

| Signal encoding | NRZ code |
|----------------------|---|
| Data transfer | 9.6 kBaud12 MBaud |
| Terminating resistor | Integrated, can be activated via DIP switches |

PROFIBUS PA

| PROFIBUS PA | In accordance with EN 50170 Volume 2, IEC 61158-2 (MBP), galvanically isolated |
|--------------------------|--|
| Data transmission | 31.25 kbit/s |
| Current consumption | 10 mA |
| Permitted supply voltage | 9 to 32 V |
| Bus connection | With integrated reverse polarity protection |

Modbus RS485

| Physical interface | RS485 in accordance with EIA/TIA-485 standard |
|----------------------|---|
| Terminating resistor | Integrated, can be activated via DIP switches |

EtherNet/IP

| Standards In accordance with IEEE 802.3 | |
|---|--|
|---|--|

PROFINET

| Standards | In accordance with IEEE 802.3 |
|-----------|-------------------------------|
|-----------|-------------------------------|

PROFINET with Ethernet-APL

| Device use | Device connection to an APL field switch The device may only be operated according to the following APL port classifications: If used in hazardous areas: SLAA or SLAC ¹⁾ If used in non-hazardous areas: SLAX |
|--------------------------|--|
| | Connection values of APL field switch (corresponds to APL port classification SPCC or SPAA, for instance): |
| | Maximum input voltage: 15 V_{DC} Minimum output values: 0.54 W |
| | Device connection to an SPE switch In non-hazardous areas, the device can be used with an appropriate SPE switch: The device can be connected to an SPE switch with a maximum voltage of 30 V_{DC} and a minimum output power of 1.85 W connected. The SPE switch must support the 10BASE-T1L standard and PoDL power classes 10, 11 or 12 and have a function to disable power class detection. |
| PROFINET | According to IEC 61158 and IEC 61784 |
| Ethernet-APL | According to IEEE 802.3cg, APL port profile specification v1.0, galvanically isolated |
| Data transmission | 10 Mbit/s |
| Current consumption | Transmitter • Max. 400 mA(24 V) • Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz) |
| Permitted supply voltage | 9 to 30 V |
| Network connection | With integrated reverse polarity protection |

1) For more information on using the device in the hazardous area, see the Ex-specific Safety Instructions

Current output 4 to 20 mA

| Order code | "Output; input 2" (21), "Output; input 3" (022): Option B: current output 4 to 20 mA |
|----------------------------------|--|
| Signal mode | Can be set to: • Active • Passive |
| Current range | Can be set to: • 4 to 20 mA NAMUR • 4 to 20 mA US • 4 to 20 mA • 0 to 20 mA (only if the signal mode is active) • Fixed current |
| Maximum output values | 22.5 mA |
| Open-circuit voltage | DC 28.8 V (active) |
| Maximum input voltage | DC 30 V (passive) |
| Load | 0 to 700 Ω |
| Resolution | 0.38 μΑ |
| Damping | Configurable: 0 to 999.9 s |
| Assignable measured variables | Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature |

Current output 4 to 20 mA Ex i passive

| Order code | "Output; input 2" (21), "Output; input 3" (022): Option C: current output 4 to 20 mA Ex i passive |
|----------------------------------|--|
| Signal mode | Passive |
| Current range | Can be set to: • 4 to 20 mA NAMUR • 4 to 20 mA US • 4 to 20 mA • Fixed current |
| Maximum output values | 22.5 mA |
| Maximum input voltage | DC 30 V |
| Load | 0 to 700 Ω |
| Resolution | 0.38 μΑ |
| Damping | Configurable: 0 to 999 s |
| Assignable measured variables | Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature |

Pulse/frequency/switch output

| Function | Can be configured as pulse, frequency or switch output |
|----------------------------------|---|
| Version | Open collector Can be set to: • Active • Passive • Passive NAMUR • Ex-i, passive |
| Maximum input values | DC 30 V, 250 mA (passive) |
| Open-circuit voltage | DC 28.8 V (active) |
| Voltage drop | For 22.5 mA: ≤ DC 2 V |
| Pulse output | |
| Maximum input values | DC 30 V, 250 mA (passive) |
| Maximum output current | 22.5 mA (active) |
| Open-circuit voltage | DC 28.8 V (active) |
| Pulse width | Configurable: 0.05 to 2 000 ms |
| Maximum pulse rate | 10000 Impulse/s |
| Pulse value | Configurable |
| Assignable measured variables | Volume flowMass flowCorrected volume flow |
| Frequency output | |
| Maximum input values | DC 30 V, 250 mA (passive) |
| Maximum output current | 22.5 mA (active) |
| Open-circuit voltage | DC 28.8 V (active) |
| Output frequency | Configurable: end value frequency 2 to 10000 Hz(f $_{max}$ = 12500 Hz) |

| Damping | Configurable: 0 to 999.9 s |
|----------------------------------|---|
| Pulse/pause ratio | 1:1 |
| Assignable measured variables | Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature |
| Switch output | |
| Maximum input values | DC 30 V, 250 mA (passive) |
| Open-circuit voltage | DC 28.8 V (active) |
| Switching behavior | Binary, conductive or non-conductive |
| Switching delay | Configurable: 0 to 100 s |
| Number of switching cycles | Unlimited |
| Assignable functions | Disable On Diagnostic behavior Limit value: Disable Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Totalizer 1-3 Temperature Electronics temperature Flow direction monitoring Status Empty pipe detection Buildup index HBSI limit value exceeded Low flow cut off |

Double pulse output

| Function | Double pulse |
|----------------------|--|
| Version | Open collector |
| | Can be set to: • Active • Passive • Passive NAMUR |
| Maximum input values | DC 30 V, 250 mA (passive) |
| Open-circuit voltage | DC 28.8 V (active) |
| Voltage drop | For 22.5 mA: ≤ DC 2 V |
| Output frequency | Configurable: 0 to 1 000 Hz |
| Damping | Configurable: 0 to 999 s |

| Pulse/pause ratio | 1:1 |
|----------------------------------|--|
| Assignable measured variables | Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Corrected conductivity Temperature Electronics temperature |

Relay output

| Function | Switch output |
|---|---|
| Version | Relay output, galvanically isolated |
| Switching behavior | Can be set to: • NO (normally open), factory setting • NC (normally closed) |
| Maximum switching capacity (passive) | DC 30 V, 0.1 A AC 30 V, 0.5 A |
| Assignable functions | Disable On Diagnostic behavior Limit value: Disable Volume flow Mass flow Corrected volume flow Flow velocity Conductivity Conductivity Corrected conductivity Totalizer 1-3 Temperature Electronics temperature Flow direction monitoring Status Empty pipe detection Buildup index HBSI limit value exceeded Low flow cut off |

User-configurable input/output

One specific input or output is assigned to a user-configurable input/output (configurable I/O) during device commissioning.

The following inputs and outputs are available for assignment:

- Choice of current output: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Pulse/frequency/switch output
- Choice of current input: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Status input

The technical values correspond to those of the inputs and outputs described in this section.

Signal on alarm

Depending on the interface, failure information is displayed as follows:

HART current output

Device diagnostics

Device condition can be read out via HART Command 48

PROFIBUS PA

| Status and alarm messages | Diagnostics in accordance with PROFIBUS PA Profile 3.02 |
|---|---|
| Failure current FDE (Fault Disconnection Electronic) | 0 mA |

PROFIBUS DP

| Status and alarm | Diagnostics in accordance with PROFIBUS PA Profile 3.02 |
|------------------|---|
| messages | |

EtherNet/IP

| Device diagnostics Device condition can be read out in Input Assembly |
|--|
|--|

PROFINET

| Device diagnostics | According to "Application Layer protocol for decentralized periphery", Version 2.3 |
|--------------------|--|
|--------------------|--|

PROFINET with Ethernet-APL

| Device diagnostics Diagnostics according to PROFINET PA Prome 4 | Device diagnostics | Diagnostics according to PROFINET PA Profile 4 |
|---|--------------------|--|
|---|--------------------|--|

FOUNDATION Fieldbus

| Status and alarm messages | Diagnostics in accordance with FF-891 |
|---|---------------------------------------|
| Failure current FDE (Fault Disconnection Electronic) | 0 mA |

Modbus RS485

| Failure mode | Choose from: • NaN value instead of current value |
|--------------|--|
| | Last valid value |

Modbus TCP-APL

| Failure mode | Choose from: |
|--------------|--------------------------------------|
| | NaN value instead of current value |
| | Last valid value |

Current output 0/4 to 20 mA

4 to 20 mA

| Failure mode | Choose from: 4 to 20 mA in accordance with NAMUR recommendation NE 43 4 to 20 mA in accordance with US Min. value: 3.59 mA Max. value: 22.5 mA Definable value between: 3.59 to 22.5 mA Actual value Last valid value |
|--------------|--|
|--------------|--|

0 to 20 mA

| Failure mode | Choose from: |
|--------------|--|
| | Maximum alarm: 22 mADefinable value between: 0 to 20.5 mA |

Pulse/frequency/switch output

| Pulse output | |
|------------------|---|
| Fault mode | Choose from: • Actual value • No pulses |
| Frequency output | |
| Fault mode | Choose from: • Actual value • 0 Hz • Definable value between: 2 to 12 500 Hz |
| Switch output | |
| Fault mode | Choose from: • Current status • Open • Closed |

Relay output

| Failure mode | Choose from: • Current status • Open • Closed |
|--------------|--|
| | |

Local display

| Plain text display | With information on cause and remedial measures |
|--------------------|---|
| Backlight | Red lighting indicates a device error. |

H

Status signal as per NAMUR recommendation NE 107

Interface/protocol

- Via digital communication:
 - HART protocol
 - FOUNDATION Fieldbus
 - PROFIBUS PA
 - PROFIBUS DP
 - Modbus RS485
 - Modbus TCP with Ethernet-APL
 - EtherNet/IP
 - PROFINET
 - PROFINET with Ethernet-APL
- Via service interface
 - CDI-RJ45 service interface
 - WLAN interface

Plain text display

With information on cause and remedial measures

Additional information on remote operation $\rightarrow \cong 104$

Web browser

| Plain text display | With information on cause and remedial measures |
|--------------------|---|
| | |

Light emitting diodes (LED)

| Status information | Status indicated by various light emitting diodes |
|--------------------|--|
| | The following information is displayed depending on the device version: Supply voltage active Data transmission active Device alarm/error has occurred EtherNet/IP network available EtherNet/IP connection established PROFINET network available PROFINET connection established PROFINET blinking feature |

Load

Output signal $\rightarrow \square 15$

Ex connection data

Safety-related values

| Order code "Output; input 1" | Output type | Safety-related values "Output; input 1" | |
|---------------------------------|-----------------------------------|--|--------|
| | | 26 (+) | 27 (-) |
| Option BA | Current output 4 to 20 mA HART | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | |
| Option GA | PROFIBUS PA | $U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$ | |
| Option LA | PROFIBUS DP | $U_{\rm N} = 32 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm AC}$ | |
| Option MA | Modbus RS485 | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | |
| Option MB | Modbus TCP with Ethernet-APL | $\begin{array}{l} APL \mbox{ port profile SLAX} \\ SPE \mbox{ PoDL classes 10, 11, 12} \\ U_N = 30 \ V_{DC} \\ U_M = 250 \ V_{AC} \end{array}$ | 2 |
| Option SA | FOUNDATION Fieldbus | $U_{\rm N} = 32 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | |
| Option NA | EtherNet/IP | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | |
| Option RA | PROFINET | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | |
| Option RB | PROFINET with Ethernet- APL | APL port profile SLAX SPE PoDL classes 10, 11, 12 $U_N = 30 V_{DC}$ $U_M = 250 V_{AC}$ | 2 |

| Order code | Output type | Safety-related values | | | |
|---|------------------------------------|---|--------|---------|--------|
| "Output; input 2"; "Output; input 3" | | Output; input 2 Output; input 3 | | input 3 | |
| | | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Option B | Current output 4 to 20 mA | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | 2 | | |
| Option D | User-configurable input/ output | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | 2 | | |

| Order code | Output type | Safety-related values | | | |
|---|----------------------------------|---|---------|---------|---------|
| "Output; input 2"; "Output; input 3" | | Output; | input 2 | Output; | input 3 |
| • • • | | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Option E | Pulse/frequency/switch output | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | C | | |
| Option F | Double pulse output | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | C | | |
| Option H | Relay output | $U_{\rm N} = 30 V_{\rm DC}$ $I_{\rm N} = 100 \text{ mA}_{\rm D}$ $U_{\rm M} = 250 V_{\rm AC}$ | | | |
| Option I | Current input 4 to 20 mA | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | C | | |
| Option J | Status input | $U_{\rm N} = 30 V_{\rm DC}$ $U_{\rm M} = 250 V_{\rm AC}$ | 2 | | |

Intrinsically safe values

| Order code "Output; input 1" | Output type | Intrinsically safe values "Output; input 1" | | |
|---------------------------------|---|--|---|--|
| | | 26 (+) | 27 (-) | |
| Option CA | Current output 4 to 20 mA HART Ex i passive | $ \begin{array}{l} U_i = 30 \ V \\ l_i = 100 \ mA \\ P_i = 1.25 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array} $ | | |
| Option CC | Current output 4 to 20 mA HART Ex i active | Ex ia ¹⁾ $U_0 = 21.8 V$ $l_0 = 90 mA$ $P_0 = 491 mW$ $L_0 = 4.1 mH (IIC)/15 mH$ (IIB) $C_0 = 160 nF (IIC)/$ 1 160 nF (IIB) | Ex ic ²⁾ $U_0 = 21.8 V$ $l_0 = 90 mA$ $P_0 = 491 mW$ $L_0 = 9 mH (IIC)/39 mH$ (IIB) $C_0 = 600 nF (IIC)/$ 4000 nF (IIB) | |
| | | $ \begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 10 \ mA \\ P_{i} = 0.3 \ W \\ L_{i} = 5 \ \mu H \\ C_{i} = 6 \ nF \end{array} $ | | |
| Option HA | PROFIBUS PA Ex i (FISCO Field Device) | | Ex ic ²⁾ $U_i = 32 V$ $l_i = 570 mA$ $P_i = 8.5 W$ $L_i = 10 \mu H$ $C_i = 5 nF$ | |
| Option TA | FOUNDATION Fieldbus Ex i | | Ex ic ²⁾ $U_i = 32 V$ $l_i = 570 mA$ $P_i = 8.5 W$ $L_i = 10 \mu H$ $C_i = 5 nF$ | |
| Option RC | PROFINET with Ethernet- APL Ex i | Ex ia 1)Ex ic 2)2-WISE power load APL2-WISE power load Aport profile SLAAport profile SLAC | | |

Only available for Proline 500 transmitter Zone 1; Class I, Division 1. Only available for transmitter Zone 2; Class I, Division 2. 1) 2)

| Order code for | Output type | Intrinsically safe values or NIFW values | | | |
|---|---|---|--------|---------|--------|
| "Output; input 2"; "Output; input 3" | | Output; input 2 Output; input | | input 3 | |
| | | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| Option C | Current output 4 to 20 mA Ex i passive | $\begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 100 \ mA \\ P_{i} = 1.25 \ W \\ L_{i} = 0 \\ C_{i} = 0 \end{array}$ | | | |
| Option G | Pulse/frequency/switch output Ex i passive | $\begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 100 \ mA \\ P_{i} = 1.25 \ W \\ L_{i} = 0 \\ C_{i} = 0 \end{array}$ | | | |

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

The outputs are galvanically isolated:

- from the power supply

HART

from one another
from the potential equalization (PE) terminal

Protocol-specific data

| Manufacturer ID | 0x11 |
|---------------------------------------|--|
| Device type ID | 0x3C |
| HART protocol revision | 7 |
| Device description files (DTM, DD) | Information and files under: www.endress.com |
| HART load | Min. 250 Ω |
| System integration | Information on system integration: Operating Instructions → [□] 124. Measured variables via HART protocol Burst Mode functionality |

FOUNDATION Fieldbus

| Manufacturer ID | 0x452B48 (hex) | |
|---|--|--|
| Ident number | 0x103C (hex) | |
| Device revision | 1 | |
| DD revision | Information and files under: | |
| CFF revision | www.endress.comwww.fieldcommgroup.org | |
| Interoperability Test Kit (ITK) | Version 6.2.0 | |
| ITK Test Campaign Number | Information: • www.endress.com • www.fieldcommgroup.org | |
| Link Master capability (LAS) | Yes | |
| Choice of "Link Master" and "Basic Device" | Yes Factory setting: Basic Device | |
| Node address | Factory setting: 247 (0xF7) | |

| Supported functions | The following methods are supported: • Restart • ENP Restart • Diagnostic • Set to OOS • Set to AUTO • Read trend data |
|--------------------------------|---|
| Virtual Communication Relation | Read event logbook |
| | |
| Number of VCRs | 44 |
| Number of link objects in VFD | 50 |
| Permanent entries | 1 |
| Client VCRs | 0 |
| Server VCRs | 10 |
| Source VCRs | 43 |
| Sink VCRs | 0 |
| Subscriber VCRs | 43 |
| Publisher VCRs | 43 |
| Device Link Capabilities | |
| Slot time | 4 |
| Min. delay between PDU | 8 |
| Max. response delay | 16 |
| System integration | Information regarding system integration: Operating Instructions → ¹ 124. Cyclic data transmission Description of the modules Execution times Methods |

PROFIBUS DP

| Manufacturer ID | 0x11 |
|--|--|
| Ident number | 0x1570 |
| Profile version | 3.02 |
| Device description files (GSD, DTM, DD) | Information and files under: • https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links • https://www.profibus.com |
| Supported functions | Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur |
| Configuration of the device address | DIP switches on the I/O electronics moduleVia operating tools (e.g. FieldCare) |

| Compatibility with earlier model | If the device is replaced, the measuring device Promag 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promag 300 GSD file. |
|-------------------------------------|---|
| | Earlier models: Promag 50 PROFIBUS DP ID No.: 1546 (hex) Extended GSD file: EH3x1546.gsd Standard GSD file: EH3_1546.gsd Promag 53 PROFIBUS DP ID No.: 1526 (hex) Extended GSD file: EH3x1526.gsd Standard GSD file: EH3_1526.gsd |
| | Description of the function scope of compatibility: Operating Instructions $\rightarrow \cong 124$. |
| System integration | Information regarding system integration: Operating Instructions → ¹ 124. Cyclic data transmission Block model Description of the modules |

PROFIBUS PA

| Manufacturer ID | 0x11 | | | | | |
|--|---|--|--|--|--|--|
| Ident number | 0x156C | | | | | |
| Profile version | 3.02 | | | | | |
| Device description files (GSD, DTM, DD) | Information and files under: • https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links • https://www.profibus.com | | | | | |
| Supported functions | Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBL upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur | | | | | |
| Configuration of the device address | DIP switches on the I/O electronics module Local display Via operating tools (e.g. FieldCare) | | | | | |
| Compatibility with earlier model | If the device is replaced, the measuring device Promag 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promag 300 GSD file. | | | | | |
| | Earlier models: Promag 50 PROFIBUS PA ID No.: 1525 (hex) Extended GSD file: EH3x1525.gsd Standard GSD file: EH3_1525.gsd Promag 53 PROFIBUS PA ID No.: 1527 (hex) Extended GSD file: EH3x1527.gsd Standard GSD file: EH3_1527.gsd | | | | | |
| | Description of the function scope of compatibility: Operating Instructions $\rightarrow \cong 124$. | | | | | |
| System integration | Information regarding system integration: Operating Instructions → ● Cyclic data transmission ● Block model ● Description of the modules | | | | | |

Modbus RS485

| Protocol | Modbus Applications Protocol Specification V1.1 |
|-------------------------------------|--|
| Response times | Direct data access: typically 25 to 50 ms Auto-scan buffer (data range): typically 3 to 5 ms |
| Device type | Slave |
| Slave address range | 1 to 247 |
| Broadcast address range | 0 |
| Function codes | 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers |
| Broadcast messages | Supported by the following function codes: 06: Write single registers 16: Write multiple registers 23: Read/write multiple registers |
| Supported baud rate | 1200 BAUD 2400 BAUD 4800 BAUD 9600 BAUD 19200 BAUD 38400 BAUD 57 600 BAUD 115200 BAUD |
| Data transmission mode | ASCIIRTU |
| Data access | Each device parameter can be accessed via Modbus RS485. |
| Compatibility with earlier model | If the device is replaced, the measuring device Promag 300 supports the compatibility of the Modbus registers for the process variables and the diagnostic information with the previous model Promag 53. It is not necessary to change the engineering parameters in the automation system. Description of the function scope of compatibility: Operating Instructions → 🖺 124. |
| System integration | Information regarding system integration: Operating Instructions → 124. Modbus RS485 information Function codes Register information Response time Modbus data map |

EtherNet/IP

| Protocol | The CIP Networks Library Volume 1: Common Industrial Protocol The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP |
|---------------------------|---|
| Communication type | 10Base-T100Base-TX |
| Device profile | Generic device (product type: 0x2B) |
| Manufacturer ID | 0x000049E |
| Device type ID | 0x103C |
| Baud rates | Automatic $^{10}\!\!\gamma_{100}$ Mbit with half-duplex and full-duplex detection |
| Polarity | Auto-polarity for automatic correction of crossed TxD and RxD pairs |
| Supported CIP connections | Max. 3 connections |

| Explicit connections | Max. 6 connections | | | | | |
|--|--|--|--|--|--|--|
| I/O connections | Max. 6 connections (scanner) | | | | | |
| Configuration options for measuring device | DIP switches on the electronics module for IP addressing Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser Electronic Data Sheet (EDS) integrated in the measuring device | | | | | |
| Configuration of the EtherNet interface | Speed: 10 MBit, 100 MBit, auto (factory setting)Duplex: half-duplex, full-duplex, auto (factory setting) | | | | | |
| Configuration of the device address | DIP switches on the electronics module for IP addressing (last octet) DHCP Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser EtherNet/IP tools, e.g. RSLinx (Rockwell Automation) | | | | | |
| Device Level Ring (DLR) | Yes | | | | | |
| System integration | Information regarding system integration: Operating Instructions → ⇒ 124. Cyclic data transmission Block model Input and output groups | | | | | |

PROFINET

| Protocol | Application layer protocol for decentral device periphery and distributed automation, Version 2.3 | | | | |
|--|--|--|--|--|--|
| Communication type | 100 MBit/s | | | | |
| Conformance Class | Conformance Class B | | | | |
| Netload Class | Netload Class 2 0 Mbps | | | | |
| Baud rates | Automatic 100 Mbit/s with full-duplex detection | | | | |
| Cycle times | From 8 ms | | | | |
| Polarity | Auto-polarity for automatic correction of crossed TxD and RxD pairs | | | | |
| Media Redundancy Protocol (MRP) | Yes | | | | |
| System redundancy support | System redundancy S2 (2 AR with 1 NAP) | | | | |
| Device profile | Application interface identifier 0xF600 Generic device | | | | |
| Manufacturer ID | 0x11 | | | | |
| Device type ID | 0x843C | | | | |
| Device description files (GSD, DTM, DD) | Information and files under: • www.endress.com On the product page for the device: Documents/Software → Device drivers • www.profibus.com | | | | |
| Supported connections | 2 x AR (IO Controller AR) 1 x AR (IO-Supervisor Device AR connection allowed) 1 x Input CR (Communication Relation) 1 x Output CR (Communication Relation) 1 x Alarm CR (Communication Relation) | | | | |
| Configuration options for measuring device | DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device. Onsite operation | | | | |

| Configuration of the device name | DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server |
|----------------------------------|---|
| Supported functions | Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM) |
| System integration | Information regarding system integration: Operating Instructions → ¹ 124. Cyclic data transmission Overview and description of the modules Status coding Startup configuration Factory setting |

PROFINET with Ethernet-APL

| Protocol | Application layer protocol for decentral device periphery and distributed automation, Version 2.43 | | | | | |
|---|--|--|--|--|--|--|
| Communication type | Ethernet Advanced Physical Layer 10BASE-T1L | | | | | |
| Conformance Class | Conformance Class B (PA) | | | | | |
| Netload Class | PROFINET Netload Robustness Class 2 10 Mbit/s | | | | | |
| Baud rates | 10 Mbit/s Full-duplex | | | | | |
| Cycle times | 64 ms | | | | | |
| Polarity | Automatic correction of crossed "APL signal +" and "APL signal -" signal lines | | | | | |
| Media Redundancy Protocol (MRP) | Not possible (point-to-point connection to APL field switch) | | | | | |
| System redundancy support | System redundancy S2 (2 AR with 1 NAP) | | | | | |
| Device profile | PROFINET PA profile 4 (Application interface identifier API: 0x9700) | | | | | |
| Manufacturer ID | 17 | | | | | |
| Device type ID | 0xA43C | | | | | |
| Device description files (GSD, DTM, FDI) | Information and files available at: • www.endress.com → Downloads section • www.profibus.com | | | | | |
| Supported connections | 2x AR (IO Controller AR) 2x AR (IO Supervisor Device AR connection allowed) | | | | | |
| Configuration options for measuring device | DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device. Onsite operation | | | | | |
| Configuration of the device name | DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server | | | | | |

| Supported functions | Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM with FDI package) |
|---------------------|--|
| System integration | Information regarding system integration: Operating Instructions → ¹ 124. Cyclic data transmission Overview and description of the modules Status coding Factory setting |

Power supply

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/o | output 3 |
|----------------|-------|--|--------|----------------|--------|---------|----------|
| 1 (+) | 2 (-) | 26 (+) | 27 (-) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | The terminal assignment depends on the specific device version ordered \rightarrow 🗎 13. | | | | | |

FOUNDATION Fieldbus

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/o | output 3 |
|----------------|-------|--|--------|----------------|--------|---------|----------|
| 1 (+) | 2 (-) | 26 (A) | 27 (B) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | The terminal assignment depends on the specific device version ordered $\rightarrow \square$ 13. | | | | | |

PROFIBUS DP

| Supply voltage | | Input/output 1 | | Input/output 2 | | Input/o | output 3 |
|----------------|-------|--|--------|----------------|--------|---------|----------|
| 1 (+) | 2 (-) | 26 (B) | 27 (A) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | The terminal assignment depends on the specific device version ordered \rightarrow 🗎 13. | | | | | |

PROFIBUS PA

| Supply | voltage | Input/o | output 1 | Input/o | utput 2 | Input/c | output 3 |
|--------|---------|--|----------|---------|---------|---------|----------|
| 1 (+) | 2 (-) | 26 (B) | 27 (A) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | The terminal assignment depends on the specific device version ordered $\rightarrow \square$ 13. | | | | | |

Modbus RS485

| Supply | voltage | Input/o | output 1 | Input/o | output 2 | Input/o | output 3 |
|--------|---------|--|----------|---------|----------|---------|----------|
| 1 (+) | 2 (-) | 26 (B) | 27 (A) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | The terminal assignment depends on the specific device version ordered $\rightarrow \square$ 13. | | | | | |

Modbus TCP with Ethernet-APL

| Supply | voltage | Input/o | output 1 | Input/o | output 2 | Input/o | output 3 |
|--------|---------|--|----------|---------|----------|---------|----------|
| 1 (+) | 2 (-) | 26 (+) | 27 (-) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | The terminal assignment depends on the specific device version ordered $\rightarrow \square$ 13. | | | | | |

PROFINET


| Supply | Supply voltage Input/output 1 | | Input/c | output 2 | Input/o | output 3 |
|--------|-------------------------------|------------------------------|---------|----------|--|----------|
| 1 (+) | 2 (-) | PROFINET (RJ45 connector) | | 5 | 22 (+) t depends on t rdered → 🗎 1 | |

PROFINET with Ethernet-APL

| Supply | voltage | Input/o | output 1 | Input/o | output 2 | Input/o | output 3 |
|--------|---------|--|----------|---------|----------|---------|----------|
| 1 (+) | 2 (-) | 26 (+) | 27 (-) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | The terminal assignment depends on the specific device version ordered \rightarrow 🗎 13. | | | | | |

EtherNet/IP

| Supply voltage | | Input/output 1 | Input/output 2 | | Input/output 3 | |
|----------------|-------|---------------------------------|----------------|--------|--------------------------------|--------|
| 1 (+) | 2 (-) | EtherNet/IP (RJ45 connector) | 24 (+) | 25 (-) | 22 (+) | 23 (-) |
| | | (RJ45 connector) | | 5 | t depends on t rdered → 🗎 1 | * |



Terminal assignment of the remote display and operating module $\rightarrow \cong$ 36.

1

Device plugs may not be used in hazardous areas!

Device plugs for fieldbus systems:

Order code for "Input; output 1"

- Option NA "EtherNet/IP" → 🖺 33
- Option **RA** "PROFINET" \rightarrow \cong 34
- Option **RB** "PROFINET with Ethernet-APL" \rightarrow \cong 34

Device plug for connecting to the service interface: Order code for "Accessory mounted" Option NB, RJ45 M12 adapter (service interface) \rightarrow \cong 47

Order code for "Input; output 1", option SA "FOUNDATION Fieldbus"

| Order code for | Cable entry/connection $\rightarrow \cong 35$ | | |
|-------------------------|---|---|--|
| "Electrical connection" | 2 | 3 | |
| M, 3, 4, 5 | 7/8" connector | - | |

Order code for "Input; output 1", option GA "PROFIBUS PA"

| Order code for | Cable entry/con | nection $\rightarrow \cong 35$ |
|-------------------------|-------------------|--------------------------------|
| "Electrical connection" | 2 | 3 |
| L, N, P, U | Connector M12 × 1 | - |

Order code for "Input; output 1", option NA "EtherNet/IP"

| Order code for | Cable entry/connection → 🗎 35 | | |
|---|-------------------------------|-------------------|--|
| "Electrical connection" | 2 | 3 | |
| L, N, P, U | Connector M12 × 1 | - | |
| R ¹⁾²⁾ , S ¹⁾²⁾ , T ¹⁾²⁾ , V ¹⁾²⁾ | Connector M12 × 1 | Connector M12 × 1 | |

1) Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001

2) Suitable for integrating the device in a ring topology.

Order code for "Input; output 1", option RA "PROFINET"

| Order code for | Cable entry/connection $\rightarrow \cong 35$ | | |
|---|---|-------------------|--|
| "Electrical connection" | 2 | 3 | |
| L, N, P, U | Connector M12 × 1 | - | |
| R ¹⁾²⁾ , S ¹⁾²⁾ , T ¹⁾²⁾ , V ¹⁾²⁾ | Connector M12 × 1 | Connector M12 × 1 | |

1) Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001.

2) Suitable for integrating the device in a ring topology.


Order code for "Input; output 1", option RB "PROFINET with Ethernet-APL"

| Order code | Cable entry/connection $\rightarrow \triangleq 35$ | | |
|-------------------------|--|---|--|
| "Electrical connection" | 2 | 3 | |
| L, N, P, U | M12 plug × 1 | - | |


Order code for "Accessory mounted", option NB "Adapter RJ45 M12 (service interface)"


| Order code | Cable entry/coupling $\rightarrow \cong 35$ | | |
|---------------------|---|------------------|--|
| "Accessory mounted" | Cable entry 2 | Cable entry 3 | |
| NB | Plug M12 × 1 | - | |

| Supply voltage | Order code "Power supply" | Terminal voltage | 2 | Frequency range | |
|-----------------------------------|---|---|---------|-----------------|--|
| | Option D | DC 24 V | ±20% | - | |
| | Option E | AC 100 to 240 V | -15+10% | 50/60 Hz, ±4 Hz | |
| | Option I | DC 24 V | ±20% | - | |
| | | AC 100 to 240 V | -15+10% | 50/60 Hz, ±4 Hz | |
| Power consumption | Transmitter | | | | |
| | Max. 10 W (active power) | | | | |
| | switch-on current | Max. 36 A (<5 ms) as per NAMUR Recommendation NE 21 | | | |
| Current consumption | Transmitter | | | | |
| | Max. 400 mA (24 V) Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz) | | | | |
| Power supply failure | Totalizers stop at the last value measured. Depending on the device version, the configuration is retained in the device memory or in the pluggable data memory (HistoROM DAT). Error messages (incl. total operated hours) are stored. | | | | |
| Overcurrent protection element | The device must be operated with a dedicated circuit breaker, as it does not have an ON/OFF switch of its own. The circuit breaker must be easy to reach and labeled accordingly. Permitted nominal current of the circuit breaker: 2 A up to maximum 10 A. | | | | |



Transmitter connection





- 1 Terminal connection for supply voltage
 - Terminal connection for signal transmission, input/output
- 3 Terminal connection for signal transmission, input/output or terminal for network connection via service interface (CDI-RJ45); Optional: terminal connection for external WLAN antenna or connection for remote display and operating module DKX001
- 4 Terminal connection for potential equalization (PE)



2

An adapter for the RJ45 to the M12 plug is optionally available:

Order code for "Accessories", option **NB**: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can therefore be established via an M12 plug without opening the device.




Network connection via service interface (CDI-RJ45) \rightarrow 🗎 110


Connecting in a ring topology

Device versions with EtherNet/IP and PROFINET communication protocols can be integrated into a ring topology. The device is integrated via the terminal connection for signal transmission (output 1) and the connection to the service interface (CDI-RJ45).

- Integrate the transmitter into a ring topology:
 - EtherNet/IP
 - PROFINET



- 1 Terminal connection for supply voltage
- 2 Terminal connection for signal transmission: PROFINET or EtherNet/IP (RJ45 connector)
- 3 Terminal connection to service interface (CDI-RJ45)
- 4 Terminal connection for potential equalization (PE)




A002678

Connecting the remote display and operating module DKX001

The remote display and operating module DKX001 is available as an optional extra $\rightarrow \square$ 121..

- The remote display and operating module DKX001 is only available for the following housing version: order code for "Housing": option A "Aluminum, coated"
- The measuring instrument is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring instrument. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring instrument display module. Only one display or operation unit may be connected to the transmitter at any one time.




- *1 Remote display and operating module DKX001*
- 2 Terminal connection for potential equalization (PE)
- 3 Connecting cable

-

- 4 Measuring instrument
- 5 Terminal connection for potential equalization (PE)


Connection examples

Current output 4 to 20 mA HART




2 Connection example for 4 to 20 mA HART current output (active)

- 1 Automation system with current input (e.g. PLC)
- 2 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications $\rightarrow \square 47$
- 3 Connection for HART operating devices $\rightarrow \square 104$
- 4 Resistor for HART communication ($\geq 250 \Omega$): observe maximum load $\rightarrow \square 15$
- 5 Analog display unit: observe maximum load $\rightarrow \square 15$
- 6 Transmitter




- ☑ 3 Connection example for 4 to 20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications $\rightarrow \textcircled{B}$ 47
- 4 Analog display unit: observe maximum load $\rightarrow \square 15$
- 5 Transmitter

HART input



- Connection example for HART input with a common negative (passive)
- 1 Automation system with HART output (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 Analog display unit: observe maximum load $\rightarrow \square 15$
- 5 Pressure measuring device (e.g. Cerabar M, Cerabar S): observe requirements
- 6 Transmitter


PROFIBUS PA



☑ 5 Connection example for PROFIBUS PA

- 1 Control system (e.g. PLC)
- 2 PROFIBUS PA segment coupler
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line

PROFIBUS DP




Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter


If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

EtherNet/IP




- ☑ 7 Connection example for EtherNet/IP
- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter

EtherNet/IP: DLR (Device Level Ring)




- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications $\rightarrow \implies 47$
- 4 Transmitter
- 5 Connecting cable between the two transmitters

PROFINET



- 8 Connection example for PROFINET
- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- *3 Observe cable specifications*
- 4 Device plug
- 5 Transmitter


PROFINET with Ethernet-APL



🛃 9 Connection example for PROFINET with Ethernet-APL


- 1 Cable shield
- 2 Measuring device
- 3 Local grounding
- Potential equalization Trunk or TCP 4
- 5
- 6 Field switch

PROFINET: MRP (Media Redundancy Protocol)



- Control system (e.g. PLC) Ethernet switch 1
- 2
- 3 *Observe cable specifications* $\rightarrow \square 47$
- Transmitter 4
- 5 Connecting cable between the two transmitters


PROFINET: system redundancy S2



10 Connection example for system redundancy S2


- 1 Control system 1 (e.g. PLC)
- Synchronization of control systems 2
- 3 Control system 2 (e.g. PLC)
- Industrial Ethernet Managed Switch 4
- 5 Transmitter

FOUNDATION Fieldbus



- 🖻 11 Connection example for FOUNDATION Fieldbus
- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus) 2
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- Local grounding 6
- 7 Bus terminator
- 8 Potential matching line


Modbus RS485



💽 12 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC 2 requirements; observe cable specifications
- Distribution box
- 3 4 Transmitter


Modbus with TCP-APL



🖻 13 Connection example for Modbus with TCP-APL


- 1
- Cable shield Measuring device 2
- 3 Local grounding
- Potential equalization Trunk or TCP 4
- 5
- 6 Field switch

Current output 4-20 mA



■ 14 Connection example for 4-20 mA current output (active)


- 1 Automation system with current input (e.g. PLC)
- 2 Analog display unit: observe maximum load $\rightarrow \square 15$
- 3 Transmitter



15 Connection example for 4-20 mA current output (passive)


- 1 Automation system with current input (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- *3* Analog display unit: observe maximum load $\rightarrow \square 15$
- 4 Transmitter


Pulse/frequency output



- 16 Connection example for pulse/frequency output (passive)
- 1 Automation system with pulse/frequency input (e.g. PLC with 10 k Ω pull-up or pull-down resistor)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \cong 18$


Switch output






- 1 Automation system with switch input (e.g. PLC with a 10 k Ω pull-up or pull-down resistor)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \square 18$

Double pulse output



■ 18 Connection example for double pulse output (active)


- 1 Automation system with double pulse input (e.g. PLC)
- 2 Transmitter: observe input values $\rightarrow \square 19$
- 3 Double pulse output
- 4 Double pulse output (slave), phase-shifted



Connection example for double pulse output (passive)

- 1 Automation system with double pulse input (e.g. PLC with a 10 k Ω pull-up or pull-down resistor)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \square 19$
- 4 Double pulse output
- 5 Double pulse output (slave), phase-shifted


Relay output






- Automation system with relay input (e.g. PLC) 1
- 2 Power supply
- 3 *Transmitter: observe input values* $\rightarrow \cong 20$

Current input



- 🖻 21 Connection example for 4 to 20 mA current input
- Power supply 1
- 2 Terminal box
- 3 External measuring device (to read in pressure or temperature, for instance)
- 4 Transmitter

Status input



🛃 22 Connection example for status input

- Automation system with status output (e.g. PLC) 1
- 2 3 Power supply
- Transmitter

Terminals

Spring-loaded terminals: Suitable for strands and strands with ferrules. Conductor cross-section 0.2 to 2.5 mm^2 (24 to 12 AWG).

Cable entries

- Cable gland: M20 \times 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
- NPT ¹/₂"
- G ½"
- M20
- Device plug for digital communication: M12 Only available for certain device versions $\rightarrow \implies$ 33.

Pin assignment, device plug

FOUNDATION Fieldbus

| Pin | | Assignment | Coding | Plug/socket |
|-----|---|--------------|--------|-------------|
| 1 | + | Signal + | А | Plug |
| 2 | - | Signal – | | |
| 3 | | Grounding | | |
| 4 | | Not assigned | | |

PROFIBUS PA

| Pin | | Assignment | Coding | Plug/socket |
|-----|---|---------------|--------|-------------|
| 1 | + | PROFIBUS PA + | А | Plug |
| 2 | | Grounding | | |
| 3 | - | PROFIBUS PA - | | |
| 4 | | Not assigned | | |

- Recommended plug: Binder, series 713, part no. 99 1430 814 04
 - Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

PROFINET

| 2 | Pin | | Assignment |
|---------------|-----|------|-------------|
| | 1 | + | TD + |
| | 2 | + | RD + |
| | 3 | - | TD - |
| | 4 | - | RD - |
| 4 A0032047 | Cod | ling | Plug/socket |
| | Ι |) | Socket |

- Recommended plug: Binder, series 825, part no. 99 3729 810 04
 - Phoenix, part no. 1543223 SACC-M12MSD-4Q


PROFINET with Ethernet-APL

| | Pin | Assignment | Coding | Plug/socket |
|-------|--|---------------------------|--------|-------------|
| 3 - 4 | 1 | APL signal - | А | Socket |
| | 2 | APL signal + | | |
| | 3 | Cable shield ¹ | | |
| | 4 | Not used | | |
| | Metal plug housing | Cable shield | | |
| | ¹ If a cable shield is used | | | |

Recommended plug:

- Binder, series 713, part no. 99 1430 814 04
- Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

EtherNet/IP




Recommended plug:

- Binder, series 825, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q

Service interface for

Order code for "Accessories mounted", option NB: Adapter RJ45 M12 (service interface)



Recommended plug:

Binder, series 825, part no. 99 3729 810 04

Phoenix, part no. 1543223 SACC-M12MSD-4Q

Cable specification

Permitted temperature range

- The installation guidelines that apply in the country of installation must be observed.
- The cables must be suitable for the minimum and maximum temperatures to be expected.

Power supply cable (incl. conductor for the inner ground terminal)

Standard installation cable is sufficient.

Protective grounding cable for the outer ground terminal

Conductor cross-section < 2.1 mm² (14 AWG)

The use of a cable lug enables the connection of larger cross-sections.

The grounding impedance must be less than 2 Ω .

Signal cable

Current output 4 to 20 mA HART

A shielded cable is recommended. Observe grounding concept of the plant.

PROFIBUS PA

Twisted, shielded two-wire cable. Cable type A is recommended .

For further information on planning and installing PROFIBUS networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

| Cable type | A | |
|--------------------------|--|--|
| Characteristic impedance | 135 to 165 Ω at a measuring frequency of 3 to 20 MHz | |
| Cable capacitance | < 30 pF/m | |
| Wire cross-section | > 0.34 mm ² (22 AWG) | |
| Cable type | Twisted pairs | |
| Loop resistance | ≤110 Ω/km | |
| Signal damping | Max. 9 dB over the entire length of the cable cross-section | |
| Shield | Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant. | |

For further information on planning and installing PROFIBUS networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.

For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization

PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.

For more information on planning and installing PROFINET networks, see: "PROFINET Cabling and Interconnection Technology", Guideline for PROFINET

PROFINET over Ethernet-APL

The reference cable type for APL segments is fieldbus cable type A, MAU type 1 and 3 (specified in IEC 61158-2). This cable meets the requirements for intrinsically safe applications according to IEC TS 60079-47 and can also be used in non-intrinsically safe applications.

| Cable type | A | | |
|-------------------|----------------|--|--|
| Cable capacitance | 5 to 200 nF/km | | |
| Loop resistance | .5 to 150 Ω/km | | |
| Cable inductance | D.4 to 1 mH/km | | |

Further details are provided in the Ethernet-APL Engineering Guideline (https://www.ethernet-apl.org).

Modbus TCP-APL

The reference cable type for APL segments is fieldbus cable type A, MAU type 1 and 3 (specified in IEC 61158-2). This cable meets the requirements for intrinsically safe applications according to IEC TS 60079-47 and can also be used in non-intrinsically safe applications.

| Cable type | A | |
|-------------------|-----------------|--|
| Cable capacitance | 45 to 200 nF/km | |
| Loop resistance | 5 to 150 Ω/km | |
| Cable inductance | 0.4 to 1 mH/km | |

Further details are provided in the Ethernet-APL Engineering Guideline (https://www.ethernet-apl.org).

FOUNDATION Fieldbus

Twisted, shielded two-wire cable.

For further information on planning and installing FOUNDATION Fieldbus networks see:

- Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)
- FOUNDATION Fieldbus Guideline
- IEC 61158-2 (MBP)

Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

| Cable type | A | |
|--------------------------|--|--|
| Characteristic impedance | 135 to 165 Ω at a measuring frequency of 3 to 20 MHz | |
| Cable capacitance | < 30 pF/m | |
| Wire cross-section | > 0.34 mm ² (22 AWG) | |
| Cable type | Twisted pairs | |
| Loop resistance | ≤110 Ω/km | |
| Signal damping | Max. 9 dB over the entire length of the cable cross-section | |
| Shield | Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant. | |

Current output 0/4 to 20 mA

Standard installation cable is sufficient.

Pulse /frequency /switch output

Standard installation cable is sufficient.

Double pulse output

Standard installation cable is sufficient.

Relay output

Standard installation cable is sufficient.

Current input 0/4 to 20 mA

Standard installation cable is sufficient.

Status input

Standard installation cable is sufficient.

Connecting cable for transmitter - remote display and operating module DKX001

Standard cable

A standard cable can be used as the connecting cable.

| Standard cable | 4 cores (2 pairs); pair-stranded with common shield | |
|--------------------------|---|--|
| Shielding | Tin-plated copper-braid, optical cover ≥ 85 % | |
| Capacitance: core/shield | Maximum 1 000 nF for Zone 1; Class I, Division 1 | |
| L/R | Maximum 24 $\mu H/\Omega$ for Zone 1; Class I, Division 1 | |
| Cable length | Maximum 300 m (1000 ft), see the following table | |

| Cross-section | Cable length for use in: Non-hazardous area Hazardous area: Zone 2; Class I, Division 2 Hazardous area: Zone 1; Class I, Division 1 |
|-------------------------------|--|
| 0.34 mm ² (22 AWG) | 80 m (270 ft) |
| 0.50 mm ² (20 AWG) | 120 m (400 ft) |
| 0.75 mm ² (18 AWG) | 180 m (600 ft) |
| 1.00 mm ² (17 AWG) | 240 m (800 ft) |
| 1.50 mm ² (15 AWG) | 300 m (1000 ft) |

Optionally available connecting cable

| Standard cable | $2\times2\times0.34~mm^2$ (22 AWG) PVC cable $^{1)}$ with common shield (2 pairs, pair-stranded) | |
|--------------------------|--|--|
| Flame resistance | According to DIN EN 60332-1-2 | |
| Oil-resistance | According to DIN EN 60811-2-1 | |
| Shielding | Tin-plated copper-braid, optical cover \geq 85 % | |
| Capacitance: core/shield | <200 pF/m | |
| L/R | <24 μH/Ω | |
| Available cable length | 10 m (35 ft) | |
| Operating temperature | When mounted in a fixed position: –50 to +105 $^\circ C$ (–58 to +221 $^\circ F); when cable can move freely: –25 to +105 ^\circ C (–13 to +221 ^\circ F)$ | |

1) UV radiation can impair the cable outer sheath. Protect the cable from direct sunshine where possible.

Overvoltage protection

| Mains voltage fluctuations | → 🗎 34 |
|-----------------------------------|---|
| Overvoltage category | Overvoltage category II |
| Short-term, temporary overvoltage | Between cable and ground up to 1200 V, for max. 5 s |
| Long-term, temporary overvoltage | Between cable and ground up to 500 V |

Performance characteristics

| Reference operating conditions | Error limits following DIN EN 29104, in future ISO 20456 Water, typically: +15 to +45 °C (+59 to +113 °F); 0.5 to 7 bar (73 to 101 psi) |
|--------------------------------|--|
| | Data as indicated in the calibration protocol |
| | Accuracy based on accredited calibration rigs according to ISO 17025 |
| | Poteroneo temporaturo for conductivity moneyrement: 25 °C (77 °E) |

Reference temperature for conductivity measurement: 25 °C (77 °F)

Maximum measurement error


o.r. = of reading

Maximum permissible error under reference operating conditions

Volume flow

- ±0.5 % o.r. ± 1 mm/s (0.04 in/s)
- Optional: ±0.2 % o.r. ± 2 mm/s (0.08 in/s)

Fluctuations in the supply voltage do not have any effect within the specified range.



■ 23 Maximum measured error in % o.r.

Temperature

±3 °C (±5.4 °F)


Electrical conductivity

The values apply for:


- Devices with stainless steel process connections
- Measurements at a reference temperature of 25 °C (77 °F). At different temperatures, attention
 must be paid to the temperature coefficient of the medium (typically 2.1 %/K)

| Conductivity | Nominal | diameter | Measurement error |
|---------------------|-----------|--|---|
| [µS/cm] | [mm] [in] | | [%] of reading |
| 5 to 20 | 15150 | 1⁄26 | ± 20% |
| > 20 to 50 | 15150 | 1⁄26 | ± 10% |
| > 50 to 10 000 | 28 | ¹ / ₁₂ to ⁵ / ₁₆ | ± 10% |
| | 15150 | ¹ /26 | Standard: ± 10% Optional ¹): ± 5% |
| > 10000 to 20000 | 2150 | ¹ / ₁₂ to 6 | ± 10% |
| > 20 000 to 100 000 | 2150 | ¹ / ₁₂ to 6 | ± 20% |

1) Order code for "Calibrated conductivity measurement", option CW



☑ 24 Measurement error (standard)



☑ 25 Measurement error (optional: order code for "Calibrated conductivity measurement", option CW)

Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

|--|

Pulse/frequency output

o.r. = of reading

| | Accuracy | Max. ± 50 ppm o.r. (over the entire ambient temperature range) |
|---------------------------------------|---|---|
| Repeatability | o.r. = of reading | |
| | Volume flow Max. ±0.1 % o.r. ± 0.5 mi | m/s (0.02 in/s) |
| | Temperature ±0.5 °C (±0.9 °F) | |
| | Electrical conductivity Max. ±5 % o.r. Max. ±1 % o.r. for DN 2 1.4404 (F316L) | 15 to 150 in conjunction with process connections made of stainless steel |
| Temperature measurement response time | T ₉₀ < 15 s | |

 Influence of ambient temperature
 Current output

 Temperature coefficient
 Max. 1 μA/°C


 Pulse/frequency output
 Temperature coefficient

 Temperature coefficient
 No additional effect. Included in accuracy.


Mounting

Mounting location

- Do not install the device at the highest point of the pipe.
- Do not install the device upstream from a free pipe outlet in a down pipe.



The device should ideally be installed in an ascending pipe.



Installation upstream from a down pipe


NOTICE

Negative pressure in the measuring pipe can damage the liner!

• If installing upstream of down pipes whose length $h \ge 5$ m (16.4 ft): install a siphon with a vent valve downstream of the device.




This arrangement prevents the flow of liquid stopping in the pipe and air entrainment.



- 1 Vent valve
- 2 Pipe siphon
- h Length of down pipe

Installation with partially filled pipes

- Partially filled pipes with a gradient require a drain-type configuration.
- The installation of a cleaning valve is recommended.




Installation near pumps

NOTICE

Negative pressure in the measuring tube can damage the liner!

- In order to maintain the system pressure, install the device in the flow direction downstream from the pump.
- Install pulsation dampers if reciprocating, diaphragm or peristaltic pumps are used.



• Information on the liner's resistance to partial vacuum


• Information on the measuring system's resistance to vibration and shock \rightarrow

Installation in event of pipe vibrations

NOTICE

Pipe vibrations can damage the device!

- ▶ Do not expose the device to strong vibrations.
- Support the pipe and fix it in place.
- Support the device and fix it in place.





Information on the measuring system's resistance to vibration and shock ightarrow 🖺 58

Orientation

The direction of the arrow on the nameplate helps you to install the measuring device according to the flow direction (direction of medium flow through the piping).

| Orien | tation | Recommendation |
|---|--------------------------|--|
| Vertical orientation | | |
| Horizontal orientation | <u>- ε α</u> Α0041328 | ✓ 1) |
| Horizontal orientation, transmitter at bottom | A0015590 | √ √ ²⁾ 3) ★ 4) |
| Horizontal orientation, transmitter at side | A0015592 | × |

- 1) The measuring device should be self-draining for hygiene applications. A vertical orientation is recommended for this. If only a horizontal orientation is possible, an angle of inclination $\alpha \ge 10^{\circ}$ is recommended.
- 2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.
- 3) To prevent the electronics from overheating in the event of strong heat formation (e.g. CIP or SIP cleaning process), install the device with the transmitter part pointing downwards.
- 4) With the empty pipe detection function switched on: empty pipe detection only works if the transmitter housing is pointing upwards.

Vertical

Optimum for self-emptying pipe systems and for use in conjunction with empty pipe detection.

| | A0015591 |
|-----------------------|--|
| | Horizontal |
| | Ideally, the measuring electrode plane should be horizontal. This prevents brief insulation of the measuring electrodes by entrained air bubbles. Empty pipe detection only works if the transmitter housing is pointing upwards as otherwise there is no guarantee that the empty pipe detection function will actually respond to a partially filled or empty measuring tube. |
| | |
| | EPD electrode for empty pipe detection, available from ≥ DN 15 (½") Measuring electrodes for signal detection Measuring instruments with a nominal diameter < DN 15 (½") do not have an EPD electrode. In this case, empty pipe detection is performed via the measuring electrodes. |
| Inlet and outlet runs | Installation with inlet and outlet runs |
| | To avoid a vacuum and to maintain the specified level of measurement accuracy, install the device upstream from assemblies that produce turbulence (e.g. valves, T-sections) and downstream from pumps. |
| | Maintain straight, unimpeded inlet and outlet runs. |
| | |
| | |
| | A0028997 |
| | |

 \sim

11

A0042132

Adapters


The sensor can also be installed in larger-diameter pipes with the aid of suitable adapters according to DIN EN 545 (double-flange reducers). The resultant increase in the rate of flow improves measuring accuracy with very slow-moving fluids.

The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders:

- Calculate the ratio of the diameters d/D.
- From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.




• If the medium has a high viscosity, a larger measuring tube diameter can be considered in order to reduce pressure loss.



Special mounting instructions

Weather protection cover



🗷 26 Engineering unit mm (in)

Hygienic compatibility

• When installing in hygienic applications, please refer to the information in the "Certificates and approvals/hygienic compatibility" section $\rightarrow \cong 116$


 In the case of measuring devices with the order code for "Housing", option B "Stainless, hygienic", to seal the connection compartment cover, screw it closed finger-tight and tighten it by another 45° (corresponds to 15 Nm).

Ambient temperature range Transmitter Standard: -40 to +60 °C (-40 to +140 °F) Local display -20 to +60 °C (-4 to +140 °F), the readability of the display may be impaired at temperatures outside the temperature range. -40 to +60 °C (-40 to +140 °F) Sensor Liner Do not exceed or fall below the permitted temperature range of the liner. If operating outdoors: Install the measuring device in a shady location. • Avoid direct sunlight, particularly in warm climatic regions. Avoid direct exposure to weather conditions. You can order a weather protection cover from Endress+Hauser. $\rightarrow \square$ 121. Storage temperature The storage temperature corresponds to the operating temperature range of the transmitter and the sensor $\rightarrow \blacksquare 58$. • Protect the measuring device against direct sunlight during storage in order to avoid unacceptably high surface temperatures. • Select a storage location where moisture cannot collect in the measuring device as fungus or bacteria infestation can damage the liner. If protection caps or protective covers are mounted these should never be removed before installing the measuring device. Additional protection against condensation and moisture: the sensor housing is potted with a gel. Atmosphere Order code for "Sensor option", option CF "Harsh environment". **Relative humidity** The device is suitable for use outdoors and indoors with a relative humidity of 4 to 95 %. **Operating height** According to EN 61010-1 $\leq 2\,000\,\mathrm{m}\,(6\,562\,\mathrm{ft})$ > 2 000 m (6562 ft) with additional overvoltage protection (e.g. Endress+Hauser HAW Series) Degree of protection Transmitter • IP66/67, Type 4X enclosure, suitable for pollution degree 4 • When the housing is open: IP20, Type 1 enclosure, suitable for pollution degree 2 • Display module: IP20, Type 1 enclosure, suitable for pollution degree 2 Optional External WLAN antenna IP67 Vibration sinusoidal, in accordance with IEC 60068-2-6 Vibration-resistance and shock-resistance 2 to 8.4 Hz, 3.5 mm peak • 8.4 to 2000 Hz, 1 q peak Vibration broad-band random, according to IEC 60068-2-64 10 to 200 Hz, 0.003 g²/Hz 200 to 2 000 Hz, 0.001 g²/Hz • Total: 1.54 g rms Shock half-sine, according to IEC 60068-2-27 6 ms 30 q Rough handling shocks according to IEC 60068-2-31

Environment

| Internal cleaning | CIP cleaningSIP cleaning |
|--|--|
| Mechanical load | Transmitter housing: Protect against mechanical effects, such as shock or impact Do not use as a ladder or climbing aid |
| Electromagnetic compatibility (EMC) | As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) As per IEC/EN 61000-6-2 and IEC/EN 61000-6-4 Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170 Volume 2, IEC 61784 |
| | The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible. |
| | Details are provided in the Declaration of Conformity. |
| | This unit is not intended for use in residential environments and cannot guarantee adequate protection of the radio reception in such environments. |

Process




Pressure/temperature ratings


The following graphics contain material load diagrams (reference curves) for different process connections in relation to the medium temperature.


Process connections with O-ring seal, DN 2 to 25 (1/12 to 1")

Process connection: welding nipple similar to DIN EN ISO 1127, ISO 2037; coupling similar to ISO 228/DIN 2999, NPT




27 Process connection material: stainless steel, 1.4404 (F316L)






🖻 28 Process connection material: stainless steel, 1.4404 (F316L)




29 Process connection material: PVDF




☑ 30 Process connection material: PVC-U






🖻 31 Process connection material: stainless steel, 1.4404 (F316L)




■ 32 Process connection material: PVDF

Process connection: flange similar to JIS B2220




■ 33 Process connection material: stainless steel, 1.4404 (F316L)



34 Process connection material: PVDF

Process connections with aseptic gasket seal, DN 2 to 25 (1/12 to 1")


Process connection: welding nipple similar to EN 10357, ASME BPE, ISO 2037; clamp similar to ISO 2852, DIN 32676; coupling similar to DIN 11851, DIN 11864-1, SMS 1145; flange similar to DIN 11864-2




☑ 35 Process connection material: stainless steel, 1.4404 (F316L)

Process connections with a septic gasket seal, DN 40 to 150 (1 $\frac{1}{2}$ to 6")

Process connection: coupling similar to SMS 1145




36 Process connection material: stainless steel, 1.4404 (F316L)




Process connection: welding nipple similar to EN 10357; coupling similar to DIN 11851

☑ 37 Process connection material: stainless steel, 1.4404 (F316L)




Process connection: welding nipple similar to ASME BPE

Process connection: welding nipple similar to ISO 2037




38 Process connection material: stainless steel, 1.4404 (F316L)


Process connection: clamp similar to ISO 2852, DIN 32676




☑ 39 Process connection material: stainless steel, 1.4404 (F316L)



Process connection: coupling similar to DIN 11864-1, ISO 2853





Process connection: flange similar to DIN 11864-2




41 Process connection material: stainless steel, 1.4404 (F316L)

| Pressure tightness | Liner: PFA | | | | | | | | | | |
|--------------------|--|---|--|---|----------------------|----------------------|--------------------|--|--|--|--|
| | Nominal | diameter | Limit values f | Limit values for absolute pressure in [mbar] ([psi]) for medium temperature | | | | | | | |
| | [mm] | [in] | +25 °C (+77 °F) | +80 °C (+176 °F) | +100 °C (+212 °F) | +130 °C (+266 °F) | +150 ℃ (+302 ℉) | | | | |
| | 2 to 150 | ¹ / ₁₂ to 6 | 0 (0) | 0 (0) | 0 (0) | 0 (0) | 0 (0) | | | | |
| Flow limit | optimum ve (v) to the pl • v < 2 m/s | locity of flo ysical prop (6.56 ft/s): | w is between 2 erties of the me for low conduc | tivity values | to 9.84 ft/s). Al | so match the ve | locity of flow | | | | |
| | dian In th | v > 2 m/s (6.56 ft/s): for media producing buildup (e.g. milk with a high fat content) A necessary increase in the flow velocity can be achieved by reducing the sensor nominal diameter. In the case of media with a high solids content, a sensor with a nominal diameter > DN 8 (3/8") can improve the signal stability and cleanability due to the larger electrodes. | | | | | | | | | |
| Pressure loss | No pressure loss occurs as of nominal diameter DN 8 (5/16") if the sensor is installed in with the same nominal diameter. Pressure losses for configurations incorporating adapters according to DIN EN 545 → | | | | | | | | | | |
| System pressure | | | | | | | | | | | |






Mechanical construction



Compact version



Order code for "Housing", option A "Aluminum, coated"

| DN | A 1) | B 1) | С | D | E | F | G ²⁾ | Н | I ²⁾ | К | L ³⁾ | М |
|------|------|------|------|------|------|------|-----------------|------|-----------------|-------|-----------------|------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 2 | 169 | 68 | 101 | 55 | 240 | 295 | 200 | 59 | 141 | 2.25 | 86 | 43 |
| 4 | 169 | 68 | 101 | 55 | 240 | 295 | 200 | 59 | 141 | 4.5 | 86 | 43 |
| 8 | 169 | 68 | 101 | 55 | 240 | 295 | 200 | 59 | 141 | 9 | 86 | 43 |
| 15 | 169 | 68 | 101 | 55 | 240 | 295 | 200 | 59 | 141 | 16 | 86 | 43 |
| 25 | 169 | 68 | 101 | 55 | 240 | 295 | 200 | 59 | 141 | 22.6 | 86 | 56 |
| 40 | 169 | 68 | 101 | 54 | 239 | 293 | 200 | 59 | 141 | 34.8 | 140 | 107 |
| 50 | 169 | 68 | 101 | 60 | 246 | 306 | 200 | 59 | 141 | 47.5 | 140 | 120 |
| 65 | 169 | 68 | 101 | 68 | 254 | 322 | 200 | 59 | 141 | 60.2 | 140 | 135 |
| 80 | 169 | 68 | 101 | 74 | 260 | 334 | 200 | 59 | 141 | 72.9 | 140 | 148 |
| 100 | 169 | 68 | 101 | 87 | 273 | 360 | 200 | 59 | 141 | 97.4 | 140 | 174 |
| 125 | 169 | 68 | 101 | 103 | 289 | 392 | 200 | 59 | 141 | 120.0 | 200 | 206 |
| 150 | 169 | 68 | 101 | 117 | 303 | 420 | 200 | 59 | 141 | 146.9 | 200 | 234 |

1) Depending on the cable gland used: values up to + 30 mm

2) 3) For version without local display: values – 30 mm

Total installed length depends on process connections. $\rightarrow \square 69$

| $\begin{bmatrix} \mathbf{D}\mathbf{Y} & \mathbf{A}^{1} \end{bmatrix} \begin{bmatrix} \mathbf{D} \\ \mathbf{D} \end{bmatrix} \begin{bmatrix} \mathbf{D} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{D} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{D} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C}^{2} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{V} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C}^{2} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{V} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C}^{2} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \begin{bmatrix} \mathbf{C} \\ \mathbf{C} \end{bmatrix} \end{bmatrix} $ | | | | | | | | | | | | |
|---|------|-----------------|------|------|------|------|-----------------|------|-----------------|-------|-----------------|------|
| DN | A 1) | B ¹⁾ | C | D | E | F | G ²⁾ | Н | I ²⁾ | К | L ³⁾ | М |
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 2 | 188 | 85 | 103 | 55 | 269 | 324 | 217 | 58 | 159 | 2.25 | 86 | 43 |
| 4 | 188 | 85 | 103 | 55 | 269 | 324 | 217 | 58 | 159 | 4.5 | 86 | 43 |
| 8 | 188 | 85 | 103 | 55 | 269 | 324 | 217 | 58 | 159 | 9 | 86 | 43 |
| 15 | 188 | 85 | 103 | 55 | 269 | 324 | 217 | 58 | 159 | 16 | 86 | 43 |
| 25 | 188 | 85 | 103 | 55 | 269 | 324 | 217 | 58 | 159 | 22.6 | 86 | 56 |
| 40 | 188 | 85 | 103 | 54 | 270 | 324 | 217 | 58 | 159 | 34.8 | 140 | 107 |
| 50 | 188 | 85 | 103 | 60 | 276 | 336 | 217 | 58 | 159 | 47.5 | 140 | 120 |
| 65 | 188 | 85 | 103 | 67 | 284 | 351 | 217 | 58 | 159 | 60.2 | 140 | 135 |
| 80 | 188 | 85 | 103 | 74 | 290 | 364 | 217 | 58 | 159 | 72.9 | 140 | 148 |
| 100 | 188 | 85 | 103 | 87 | 303 | 390 | 217 | 58 | 159 | 97.4 | 140 | 174 |
| 125 | 188 | 85 | 103 | 103 | 319 | 422 | 217 | 58 | 159 | 120.0 | 200 | 206 |
| 150 | 188 | 85 | 103 | 117 | 333 | 450 | 217 | 58 | 159 | 146.9 | 200 | 234 |

Order code for "Housing", option A "Aluminum, coated"; Ex d

1) Depending on the cable gland used: values up to + 30 mm

2) 3) For version without local display: values – 40 mm

Total installed length depends on process connections. $\rightarrow \cong 69$

Order code for "Housing", option B "Stainless, hygienic"


| DN | A 1) | B ¹⁾ | С | D | Е | F | G ²⁾ | н | I ²⁾ | К | L ³⁾ | М |
|------|------|-----------------|------|------|------|------|-----------------|------|-----------------|-------|-----------------|------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 2 | 183 | 73 | 110 | 55 | 254 | 309 | 207 | 65 | 142 | 2.25 | 86 | 43 |
| 4 | 183 | 73 | 110 | 55 | 254 | 309 | 207 | 65 | 142 | 4.5 | 86 | 43 |
| 8 | 183 | 73 | 110 | 55 | 254 | 309 | 207 | 65 | 142 | 9 | 86 | 43 |
| 15 | 183 | 73 | 110 | 55 | 254 | 309 | 207 | 65 | 142 | 16 | 86 | 43 |
| 25 | 183 | 73 | 110 | 55 | 254 | 309 | 207 | 65 | 142 | 22.6 | 86 | 56 |
| 40 | 183 | 73 | 110 | 54 | 255 | 309 | 207 | 65 | 142 | 34.8 | 140 | 107 |
| 50 | 183 | 73 | 110 | 60 | 261 | 321 | 207 | 65 | 142 | 47.5 | 140 | 120 |
| 65 | 183 | 73 | 110 | 67 | 269 | 336 | 207 | 65 | 142 | 60.2 | 140 | 135 |
| 80 | 183 | 73 | 110 | 74 | 275 | 349 | 207 | 65 | 142 | 72.9 | 140 | 148 |
| 100 | 183 | 73 | 110 | 87 | 288 | 375 | 207 | 65 | 142 | 97.4 | 140 | 174 |
| 125 | 183 | 73 | 110 | 103 | 304 | 407 | 207 | 65 | 142 | 120.0 | 200 | 206 |
| 150 | 183 | 73 | 110 | 117 | 318 | 435 | 207 | 65 | 142 | 146.9 | 200 | 234 |

1) Depending on the cable gland used: values up to + 30 mm

2) For version without local display: values – 30 mm


3) Total installed length depends on process connections.→ 🗎 69

Sensor flange connection



■ 43 Front view without process connections

| DN | A | В | С | D | Е | F | G | Н | К | L | М |
|------|------|------|------|------|------|------|------|------|------|------|------|
| [mm] |
| 2 | 62 | 41.6 | 34 | 9 | 24 | 42 | 43 | 8.5 | 6 | 4 | M6 |
| 4 | 62 | 41.6 | 34 | 9 | 24 | 42 | 43 | 8.5 | 6 | 4 | M6 |
| 8 | 62 | 41.6 | 34 | 9 | 24 | 42 | 43 | 8.5 | 6 | 4 | M6 |
| 15 | 62 | 41.6 | 34 | 16 | 24 | 42 | 43 | 8.5 | 6 | 4 | M6 |
| 25 | 72 | 50.2 | 44 | 26 | 29 | 55 | 56 | 8.5 | 6 | 4 | M6 |




E 44 Front view without process connections

| DN | A | В | С | D | E | F | G | Н | К | L |
|------|-------|-------|-------|------|------|------|------|------|-----------|-----------|
| | | | | | | | | | 90° ±0.5° | 60° ±0.5° |
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | Тарре | d holes |
| 40 | 99.7 | 85.8 | 71.0 | 48.3 | 34.8 | M8 | 12 | 17 | 4 | - |
| 50 | 112.7 | 98.8 | 83.5 | 60.3 | 47.5 | M8 | 12 | 17 | 4 | - |
| 65 | 127.7 | 114.8 | 100.0 | 76.1 | 60.2 | M8 | 12 | 17 | - | 6 |
| 80 | 140.7 | 133.5 | 114.0 | 88.9 | 72.9 | M8 | 12 | 17 | - | 6 |

| DN | А | В | С | D | E | F | G | Н | К | L |
|------|-------|-------|-------|-------|-------|------|------|------|-----------|-----------|
| | | | | | | | | | 90° ±0.5° | 60° ±0.5° |
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | Tappe | d holes |
| 100 | 166.7 | 159.5 | 141.0 | 114.3 | 97.4 | M8 | 12 | 17 | - | 6 |
| 125 | 198.7 | 191.5 | 171.0 | 139.7 | 120.0 | M10 | 15 | 20 | - | 6 |
| 150 | 226.7 | 219.5 | 200.0 | 168.3 | 146.9 | M10 | 15 | 20 | - | 6 |

Flange connections

Female with aseptic gasket seal





■ 45 Detail X: Asymmetrical process connection; the part shown in blue is provided by the supplier.

| DN | Suitable for pipe according to EN 10357 series | A | В | C, | D | E | L |
|----------------------|--|------|------|--------|------|------|-----|
| [mm] | A [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm |
| 2 to 8 ¹⁾ | 13 × 1.5 (DN 10) | 54 | 37 | 4 × Ø9 | 10 | 10 | 183 |
| 15 | 19 × 1.5 (DN 15) | 59 | 42 | 4 × Ø9 | 10 | 16 | 183 |
| 25 | 29 × 1.5 (DN 25) | 70 | 53 | 4 × Ø9 | 10 | 26 | 183 |

1) With DN 10 flanges as standard


Flange with notch with aseptic gasket seal





| 1.4404 | Flange DIN 11864-2, aseptic flange with notch, Form A 1.4404 (316L), suitable for pipe according to EN 10357 series A, flange with notch Order code for "Process connection", option DES/DRS | | | | | | | |
|------------|--|-----------|-----------|-----------|-----------|-----------|-----------|--|
| DN [mm] | Suitable for pipe according to EN 10357 series A [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | L [mm] | |
| 40 | 41 × 1.5 | 82 | 65 | 4 × Ø9 | 10 | 38 | 246 | |
| 50 | 53 × 1.5 | 94 | 77 | 4 × Ø9 | 10 | 50 | 246 | |
| 65 | 70 × 2 | 113 | 95 | 8 × Ø9 | 10 | 66 | 246 | |
| 80 | 85 × 2 | 133 | 112 | 8ר11 | 10 | 81 | 270 | |
| 100 | 104 × 2 | 159 | 137 | 8ר11 | 10 | 100 | 278 | |
| 125 | 129 × 2 | 183 | 161 | 8ר11 | 10 | 125 | 362 | |
| 150 | 154 × 2 | 213 | 188 | 8ר14 | 10 | 150 | 362 | |
| electrop | roughness: Ra _{max} = 0.76 μm, optional order code for volished note the internal diameters of the measuring pipe an | | - | | | | ı pigs. | |

Flanges with O-ring seal



Flange similar to EN 1092-1 (DIN 2501), Form B: PN 40 1.4404 (316L)

Order code for "Process connection", option D5S

| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | L [mm] |
|----------------------|------------------------------|-----------|-----------|-----------|-----------|-----------|
| 2 to 8 ¹⁾ | 95 | 65 | 4 × Ø14 | 16 | 17.3 | 198.4 |
| 15 | 95 | 65 | 4 × Ø14 | 16 | 17.3 | 198.4 |
| 25 | 115 | 85 | 4 × Ø14 | 18 | 28.5 | 198.4 |
| Surface roughnes | s: Ra _{max} = 1.6 µ | m | | | | |


1) DN 2 to 8 with DN 15 flanges as standard

| 1.4404 (316L) Order code for " | Process connecti | on", option A1S | 5 | | | |
|--|------------------|-----------------|-----------|-----------|-----------|-----------|
| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | L [mm] |
| 2 to 8 ¹⁾ | 90 | 60.3 | 4 × Ø15.7 | 11.2 | 15.7 | 218 |
| 15 | 90 | 60.3 | 4 × Ø15.7 | 11.2 | 15.7 | 218 |
| 25 | 110 | 79.4 | 4 × Ø15.7 | 14.2 | 26.7 | 230 |

1) DN 2 to 8 with DN 15 flanges as standard

| Flange similar to JIS/t20615, 20 K 1.4404 (316L) Order code for "Process connection", option N4S | | | | | | | | | |
|--|------------------------------|-----------|-----------|-----------|-----------|-----------|--|--|--|
| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | L [mm] | | | |
| 2 to 8 ¹⁾ | 95 | 70 | 4 × Ø15 | 14 | 15 | 220 | | | |
| 15 | 95 | 70 | 4 × Ø15 | 14 | 15 | 220 | | | |
| 25 | 125 | 90 | 4 × Ø19 | 16 | 25 | 220 | | | |
| Surface roughnes | s: Ra _{max} = 1.6 µ | m | | | | | | | |

1) DN 2 to 8 with DN 15 flanges as standard



| Lap joint flange similar to EN 1092-1 (DIN 2501): PN 16 PVDF Order code for "Process connection", option D3P | | | | | | | | |
|--|-------------|-----------|-----------|-----------|-----------|-----------|-----------|--|
| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm] | L [mm] | |
| 2 to 8 ¹⁾ | 95 | 65 | 4 x Ø14 | 14.5 | 45 | 17.3 | 200 | |
| 15 | 95 | 65 | 4 x Ø14 | 14.5 | 45 | 17.3 | 200 | |
| 25 | 115 | 85 | 4 x Ø14 | 16.5 | 68 | 28.5 | 200 | |
| Surface roughn | ess: Ra = 1 | 6 um | | | | | | |

Surface roughness: $Ra_{max} = 1.6 \ \mu m$

The required grounding rings can be ordered as accessories (order code: DK5HR-****).

1) DN 2 to 8 with DN 15 flanges as standard

Lap joint flange with grounding electrode similar to EN 1092-1 (DIN 2501): PN 16 PVDF

Order code for "Process connection", option D4P

| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm] | L [mm] |
|----------------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| 2 to 8 ¹⁾ | 95 | 65 | 4 x Ø14 | 14.5 | 45 | 17.3 | 200 |
| 15 | 95 | 65 | 4 x Ø14 | 14.5 | 45 | 17.3 | 200 |
| 25 | 115 | 85 | 4 x Ø14 | 16.5 | 68 | 28.5 | 200 |
| Surface roughn | | | | | | | |

Grounding rings are not necessary.

1) DN 2 to 8 with DN 15 flanges as standard

Lap joint flange similar to ASME B16.5: Class 150 PVDF

Order code for "Process connection", option A1P

| oraci coucyo. | 1.00000 00.00 | cettori, optio. | | | | | |
|----------------------|---------------|-----------------|------------|-----------|-----------|-----------|-----------|
| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm] | L [mm] |
| 2 to 8 ¹⁾ | 90 | 60.3 | 4 × Ø 15.7 | 15 | 35.1 | 15.7 | 200 |
| 15 | 90 | 60.3 | 4 × Ø 15.7 | 15 | 35.1 | 15.7 | 200 |
| 25 | 110 | 79.4 | 4 × Ø 15.7 | 16 | 50.8 | 26.7 | 200 |
| | | | | | | | |

Surface roughness: $Ra_{max} = 1.6 \ \mu m$

The required grounding rings can be ordered as accessories (order code: DK5HR-****).

1) DN 2 to 8 with DN 15 flanges as standard

| Order code for "Process connection", option A4P | | | | | | | | | |
|---|-----------|-----------|------------|-----------|-----------|-----------|-----------|--|--|
| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm] | L [mm] | | |
| 2 to 8 ¹⁾ | 90 | 60.3 | 4 × Ø 15.7 | 15 | 35.1 | 15.7 | 200 | | |
| 15 | 90 | 60.3 | 4 × Ø 15.7 | 15 | 35.1 | 15.7 | 200 | | |
| 25 | 110 | 79.4 | 4 × Ø 15.7 | 16 | 50.8 | 26.7 | 200 | | |

1) DN 2 to 8 with DN 15 flanges as standard

| PVDF Order code for | "Process conn | ection", optio | n N3P | | | | |
|-------------------------------|---------------|----------------|--------------|-----------|-----------|-----------|----------|
| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm] | L [mr |
| 2 to 8 ¹⁾ | 95 | 70 | 4 × Ø 15.7 | 15 | 35.1 | 15 | 20 |
| 15 | 95 | 70 | 4 × Ø 15.7 | 15 | 35.1 | 15 | 20 |
| 25 | 125 | 90 | 4 × Ø 15.7 | 16 | 50.8 | 19 | 20 |

The required grounding rings can be ordered as accessories (order code: DK5HR-****).

1) DN 2 to 8 with DN 15 flanges as standard

Lap joint flange with grounding electrode similar to JIS B2220: 10K PVDF

Order code for "Process connection", option N4P


| | | · • | | | | | |
|----------------------|---|-----------|------------|-----------|-----------|-----------|-----------|
| DN [mm] | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm] | L [mm] |
| 2 to 8 ¹⁾ | 95 | 70 | 4 × Ø 15.7 | 15 | 35.1 | 15 | 200 |
| 15 | 95 | 70 | 4 × Ø 15.7 | 15 | 35.1 | 15 | 200 |
| 25 | 125 | 90 | 4 × Ø 15.7 | 16 | 50.8 | 19 | 200 |
| Surface rough | Surface roughness: $Ra_{max} = 1.6 \ \mu m$ | | | | | | |

Grounding rings are not necessary.

1) DN 2 to 8 with DN 15 flanges as standard

Welding nipple

Welding nipple with aseptic gasket seal



Welding nipple according to EN 10357 1.4404 (316L), suitable for pipe EN 10357 series A Order code for "Process connection", option DAS

| DN [mm] | Suitable for pipe EN 10357 series A [mm] | A [mm] | B [mm] | L [mm] |
|------------|---|-----------|-----------|-----------|
| 2 to 8 | 13 × 1.5 | 13 | 10 | 132.6 |
| 15 | 19 × 1.5 | 19 | 16 | 132.6 |
| 25 | 29 × 1.5 | 29 | 26 | 132.6 |
| 40 | 41 × 1.5 | 41 | 38 | 220 |
| 50 | 53 × 1.5 | 53 | 50 | 220 |
| 65 | 70 × 2 | 70 | 66 | 220 |
| 80 | 85 × 2 | 85 | 81 | 220 |

| Welding nipple according to EN 10357 1.4404 (316L), suitable for pipe EN 10357 series A Order code for "Process connection", option DAS | | | | | | |
|---|---|-----------|-----------|-----------|--|--|
| DN [mm] | Suitable for pipe EN 10357 series A [mm] | A [mm] | B [mm] | L [mm] | | |
| 100 | 104 × 2 | 104 | 100 | 220 | | |
| 125 | 129 × 2 | 129 | 125 | 300 | | |
| 150 | 154 × 2 | 154 | 150 | 300 | | |
| Surface roughne | Surface roughness: Ra _{may} = 0.76 µm, optional order code for "Service", option HJ: Ra _{may} = 0.38 µm | | | | | |

Surface roughness: $Ra_{max} = 0.76 \ \mu m$, optional order code for "Service", option HJ: $Ra_{max} = 0.38 \ \mu m$ electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

| 1.4404 (316L), s | according to ISO 2037 uitable for pipe ISO 2037 ocess connection", option IAS | | | |
|------------------|---|-----------|-----------|-----------|
| DN [mm] | Suitable for pipe ISO 2037 [mm] | A [mm] | B [mm] | L [mm] |
| 2 to 8 | 12.7 × 1.65 | 12 | 10 | 118.2 |
| 15 | 19.05 × 1.65 | 18 | 16 | 118.2 |
| 25 | 25.4 × 1.60 | 25 | 22.6 | 118.2 |
| 40 | 38 × 1.2 | 38 | 35.6 | 220 |
| 50 | 51 × 1.2 | 51 | 48.6 | 220 |
| 65 | 63.5 × 1.6 | 63.5 | 60.3 | 220 |
| 80 | 76.1 × 1.6 | 76.1 | 72.9 | 220 |
| 100 | 101.6 × 2 | 101.6 | 97.6 | 220 |
| 125 | 139.7 × 2 | 139.7 | 135.7 | 380 |
| 150 | 168.3 × 2.6 | 168.3 | 163.1 | 380 |

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.


Welding nipple according to ASME BPE

1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C Order code for "Process connection", option **AAS**

| DN [mm] | Suitable for pipe according to ASME BPE [mm] | A [mm] | B [mm] | L [mm] |
|-----------------|--|-----------|-----------|-----------|
| 2 to 8 | 12.7 × 1.65 | 12.7 | 9 | 118.2 |
| 15 | 19.1 × 1.65 | 19.1 | 16 | 118.2 |
| 25 | 25.4 × 1.65 | 25.4 | 22.6 | 118.2 |
| 40 | 38.1 × 1.65 | 38.1 | 34.8 | 220 |
| 50 | 50.8 × 1.65 | 50.8 | 47.5 | 220 |
| 65 | 63.5 × 1.65 | 63.5 | 60.2 | 220 |
| 80 | 76.2 × 1.65 | 76.2 | 72.9 | 220 |
| 100 | 101.6 × 1.65 | 101.6 | 97.4 | 220 |
| 150 | 152.4 × 2.77 | 152.4 | 146.9 | 300 |
| electropolished | ness: Ra _{max} = 0.76 μm, optional order code for "Servi d | | | |

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Welding nipple with O-ring seal



Welding nipple according to ISO 1127 1.4404 (316L), suitable for pipe according to ISO 1127 series 1 Order code for "Process connection", option A2S DN Suitable for pipe according to ISO 1127 series 1 В L A [mm] [mm] [mm] [mm] [mm] 2 to 8 13.5 × 2.30 13.5 9 126.6 15 21.3 × 2.65 21.3 16 126.6 25 33.7 × 3.25 33.7 27.2 126.6

Surface roughness: $Ra_{max} = 1.6 \ \mu m$

Welding nipple according to ISO 1127

1.4404 (316L), suitable for pipe according to ISO 1127 series 1 and DIN 11866 series B Order code for "Process connection", option **D1S**


| DN [mm] | Suitable for pipe according to ISO 1127 series 1 and DIN 11866 series B [mm] | A [mm] | B [mm] | L [mm] |
|------------|---|-----------|-----------|-----------|
| 2 to 8 | 13.5 × 1.6 | 13.5 | 10.3 | 126.6 |
| 15 | 21.3 × 1.6 | 21.3 | 18.1 | 126.6 |
| 25 | 33.7 × 2.0 | 33.7 | 29.7 | 126.6 |
| | | | | |

Surface roughness: $Ra_{max} = 1.6 \ \mu m$

| • | itable for pipe ISO 203 cess connection", option I1S | | | |
|---|---|-----------|-----------|-----------|
| DN [mm] | Suitable for pipe ISO 2037 [mm] | A [mm] | B [mm] | L [mm] |
| 2 to 8 | 13.5 × 2.3 | 13.5 | 9 | 126.6 |
| 15 | 21.3 × 2.65 | 21.3 | 16 | 126.6 |
| 25 | 33.7 × 3.25 | 33.7 | 27.2 | 126.6 |

Clamp connections

Clamp connections with aseptic gasket seal



| l amp according t . 4404 (316L) rder code for "Proc | o DIN 32676 ress connection", option DBS | | | |
|---|--|-----------|-----------|-----------|
| DN [mm] | Suitable for pipe [mm] | A [mm] | B [mm] | L [mm] |
| 2 to 8 | 14 × 2 (DN 10) | 34 | 10 | 168 |
| 15 | 20 × 2 (DN 15) | 34 | 16 | 168 |
| 25 | 30 × 2 (DN 25) | 50.5 | 26 | 175 |
| 40 | 41 × 1.5 | 50.5 | 38 | 220 |
| 50 | 53 × 1.5 | 64 | 50 | 220 |
| 65 | 70 × 2 | 91 | 66 | 220 |
| 80 | 85 × 2 | 106 | 81 | 220 |
| 100 | 104 × 2 | 119 | 100 | 220 |
| 125 | 129 × 2 | 155 | 125 | 300 |
| 150 | 154 × 2 | 183 | 150 | 300 |

= 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm urface rougnness: Ra_{max} electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Tri-Clamp **1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C** Order code for "Process connection", option **FAS**

| DN [mm] | Suitable for pipe according to ASME BPE [mm] | A [mm] | B [mm] | L [mm] |
|------------|---|-----------|-----------|-----------|
| 2 to 8 | 12.7 × 1.65 | 25 | 9.4 | 143 |
| 15 | 19.1 × 1.65 | 25 | 15.8 | 143 |
| 25 | 25.4 × 1.65 | 50.4 | 22.1 | 143 |
| 40 | 38.1 × 1.65 | 50.4 | 34.8 | 220 |
| 50 | 50.8 × 1.65 | 63.9 | 47.5 | 220 |
| 65 | 63.5 × 1.65 | 77.4 | 60.2 | 220 |
| 80 | 76.2 × 1.65 | 90.9 | 72.9 | 220 |
| 100 | 101.6 × 2.11 | 118.9 | 97.4 | 220 |

Tri-Clamp

1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C Order code for "Process connection", option **FAS**

| DN | Suitable for pipe according to ASME BPE | A | B | L |
|------|---|-------|-------|------|
| [mm] | [mm] | [mm] | [mm] | [mm] |
| 150 | 152.4 × 2.77 | 166.9 | 146.9 | 300 |

Surface roughness: Ra_{max} = 0.76 μm , optional order code for "Service", option HJ: Ra_{max} = 0.38 μm electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Clamp according to ISO 2852, Fig. 2

1.4404 (316L)

Order code for "Process connection", option IBS


| onder code jor 1 rocess connection, option 113 | | | | | | |
|---|------------------------------------|-----------|-----------|-----------|--|--|
| DN [mm] | Suitable for pipe ISO 2037 [mm] | A [mm] | B [mm] | L [mm] | | |
| 25 | 24.5 × 1.65 | 50.5 | 22.6 | 174.6 | | |
| 40 | 38 × 1.6 | 50.5 | 35.6 | 220 | | |
| 50 | 51 × 1.6 | 64 | 48.6 | 220 | | |
| 65 | 63.5 × 1.6 | 77.5 | 60.3 | 220 | | |
| 80 | 76.1 × 1.6 | 91 | 72.9 | 220 | | |
| 100 | 101.6 × 2 | 119 | 97.6 | 220 | | |
| 125 | 139.7 × 2 | 155 | 135.7 | 300 | | |
| 150 | 168.3 × 2.6 | 183 | 163.1 | 300 | | |

Surface roughness: $Ra_{max} = 0.76 \ \mu m$, optional order code for "Service", option HJ: $Ra_{max} = 0.38 \ \mu m$ electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Couplings

Thread with aseptic gasket seal



Coupling DIN 11851, thread 1.4404 (316L), suitable for pipe EN 10357 series B Order code for "Process connection", option DCS DN Suitable for pipe EN 10357 series B Α В L [mm] [mm] [mm] [mm] [mm] 2 to 8 12 × 1 (DN 10) Rd 28 × $\frac{1}{8}$ 174 10 15 18 × 1.5 Rd 34 × 1/8 16 174 25 28 × 1 or 28×1.5 Rd 52 × $\frac{1}{6}$ 26 190

Surface roughness: $Ra_{max} = 0.76 \ \mu m$, optional order code for "Service", option HJ: $Ra_{max} = 0.38 \ \mu m$ electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

| raci couc joi | "Process connection", option DCS | | | |
|---------------|---|------------|-----------|-----------|
| DN [mm] | Suitable for pipe EN 10357 series A [mm] | A [mm] | B [mm] | L [mm] |
| 40 | 41 × 1.5 | Rd 65 × ¼ | 38 | 260 |
| 50 | 53 × 1.5 | Rd 78 × ¼ | 50 | 260 |
| 65 | 70 × 2 | Rd 95 × ¼ | 66 | 270 |
| 80 | 85 × 2 | Rd 110 × ¼ | 81 | 280 |
| 100 | 104 × 2 | Rd 130 × ¼ | 100 | 290 |
| 125 | 129 × 2 | Rd 160 × ¼ | 125 | 380 |
| 150 | 154 × 2 | Rd 160 × ¼ | 150 | 390 |

Surface roughness: $Ra_{max} = 0.76 \ \mu m$, optional order code for "Service", option HJ: $Ra_{max} = 0.38 \ \mu m$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling DIN 11864-1, aseptic thread, Form A **1.4404 (316L), suitable for pipe EN 10357 series A** Order code for "Process connection", option DDS

| order code jor | Frocess connection, option DDS | | | | | | |
|----------------|---|-------------------------------------|-----------|-----------|--|--|--|
| DN [mm] | Suitable for pipe EN 10357 series A [mm] | A [mm/in] | B [mm] | L [mm] | | | |
| 2 to 8 | 13 × 1.5 (DN 10) | Rd 28 × ¹ ⁄ ₈ | 10 | 170 | | | |
| 15 | 19 × 1.5 | Rd 34 × 1/ ₈ | 16 | 170 | | | |
| 25 | 29 × 1.5 | Rd 52 × 1/ ₆ | 26 | 184 | | | |
| 40 | 41 × 1.5 | Rd 65 × ¼ | 38 | 256 | | | |
| 50 | 53 × 1.5 | Rd 78 × ¼ | 50 | 256 | | | |
| 65 | 70 × 2 | Rd 95 × ¼ | 66 | 266 | | | |
| 80 | 85 × 2 | Rd 110 × ¼ | 81 | 276 | | | |
| 100 | 104 × 2 | Rd 130 × ¼ | 100 | 286 | | | |
| | | | | | | | |

Surface roughness: $Ra_{max} = 0.76 \ \mu m$, optional order code for "Service", option HJ: $Ra_{max} = 0.38 \ \mu m$ electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

| L.4404 (3 | SO 2853, thread 16L) for "Process connection", option IG | S | | | |
|------------|---|------------------------------|-----------------|-----------|-----------|
| DN [mm] | Suitable for pipe ISO 2037 [mm] | DN Clamp ISO 2853 [mm] | A [mm/in] | B [mm] | L [mm] |
| 40 | 38 × 1.6 | 38 | Tr 50.5 × 3.175 | 35.6 | 256 |
| 50 | 51 × 1.6 | 51 | Tr 64 × 3.175 | 48.6 | 256 |
| 65 | 63.5 × 1.6 | 63.5 | Tr 77.5 × 3.175 | 60.3 | 266 |
| 80 | 76.1 × 1.6 | 76.1 | Tr 91 × 3.175 | 72.9 | 276 |
| 100 | 101.6 × 2 | 101.6 | Tr 118 × 3.175 | 97.6 | 286 |

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling SMS 1145, thread 1.4404 (316L)


Order code for "Process connection", option SAS

| oraci coae joi i rocess connection, option and | | | | | |
|--|---------------------------|------------------------|--------------------------|-----------|-----------|
| DN [mm] | Suitable for pipe [mm] | DN SMS 1145 [mm] | A [mm/in] | B [mm] | L [mm] |
| 25 | 1 | 25 | Rd 40 × 1/ ₆ | 22.6 | 147.6 |
| 40 | 38.1 × 1.65 | 38 | Rd 60 × 1/ ₆ | 34.8 | 256 |
| 50 | 50.8 × 1.65 | 51 | Rd 70 × 1/ ₆ | 47.5 | 256 |
| 65 | 63.5 × 1.65 | 63.5 | Rd 85 × 1/ ₆ | 60.2 | 266 |
| 80 | 76.2 × 1.65 | 76 | Rd 98 × 1/ ₆ | 72.6 | 276 |
| 100 | 101.6 × 1.65 | 101.6 | Rd 132 × 1/ ₆ | 97.4 | 286 |

Surface roughness: $Ra_{max} = 0.76 \ \mu m$, optional order code for "Service", option HJ: $Ra_{max} = 0.38 \ \mu m$ electropolished

Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Thread with O-ring seal




| External thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I2S | | | | | | |
|---|--|--------------|-----------|-----------|--|--|
| DN [mm] | Suitable for internal thread ISO 228/DIN 2999 [in] | A [mm/in] | B [mm] | L [mm] | | |
| 2 to 8 | R 3⁄8 | R 10.1 × 3/8 | 10 | 166 | | |
| 15 | R 1/2 | R 13.2 × ½ | 16 | 166 | | |
| 25 | R 1 | R 16.5 × 1 | 25 | 170 | | |
| Surface roughness: | Surface roughness: Ra _{max} = 1.6 µm | | | | | |

| Internal thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I3S | | | | | | |
|---|--|--------------|-----------|-----------|--|--|
| DN [mm] | Suitable for external thread ISO 228/DIN 2999 [in] | A [mm/in] | B [mm] | L [mm] | | |
| 2 to 8 | Rp ³⁄8 | Rp 13 × 3⁄8 | 9 | 176 | | |
| 15 | Rp ⅓ | Rp 14 × ½ | 16 | 176 | | |
| 25 | Rp 1 | Rp 17 × 1 | 27.2 | 188 | | |
| Surface roughness: $Ra_{max} = 1.6 \ \mu m$ | | | | | | |

Endress+Hauser

Hose adapter


Hose adapter with O-ring seal



| Hose adapter 1.4404 (316L) Order code for "Process connection", options O1S, O2S, O3S | | | | | |
|---|--|-----------|-----------|--|--|
| DN [mm] | Suitable for internal diameter [mm] | A [mm] | L [mm] | | |
| 2 to 8 | 13 | 10 | 184 | | |
| 15 | 16 | 12.6 | 184 | | |
| 25 | 19 | 16 | 184 | | |
| Surface roughness: Ra _{max} = 1.6 µm | | | | | |

Adhesive sleeves


Adhesive sleeves with O-ring seal



| PVC Order code for "Process connection", option O2V | | | | | | |
|--|-------------------------------------|----------------|-----------|-----------|-----------|-----------|
| DN [mm] | Suitable for pipe [mm] / [in] | A [mm] | B [mm] | C [mm] | D [mm] | L [mm] |
| 2 to 8 | 20 × 2 | 62 | 38.5 | 18 | 20.2 | 163 |
| 15 | (DIN 8062) | DIN 8062) 28.0 | | 142 | | |

Mounting kits


Wall mounting kit



| A | B | C | Ø D | E | F |
|------|------|------|------|------|------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 137 | 110 | 120 | 7 | 125 | 88 |


Accessories

Weather protection cover



☑ 47 Engineering unit mm (in)

Remote display and operating module DKX001




🖻 48 Engineering unit mm (in)

External WLAN antenna

The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



■ 49 Engineering unit mm (in)


External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/ reception conditions at the transmitter mounting location are poor.






Spacer




| Order code: DK5HB-**** | | | | | | |
|------------------------|------|-------|------|------|--|--|
| DN | di | D1 | D2 | L | | |
| [mm] | [mm] | [mm] | [mm] | [mm] | | |
| 80 | 72.9 | 140.7 | 141 | 30 | | |
| 100 | 97.4 | 166.7 | 162 | 30 | | |

Clamp connections with aseptic gasket seal available for order



| Tri-Clamp 1.4404 (316L), suitable for pipe according to ASME BPE and BS 4825, reduction from pipe OD 1" (Tri- Clamp connection) to device DN 15 Order code: DKH**-HF** | | | | | | |
|---|---|-----------|-----------|-----------|--|--|
| DN [mm] | Suitable for pipe according to ASME BPE and BS 4825 (reduction) [mm] | A [mm] | B [mm] | L [mm] | | |
| 15 | Pipe OD 1" | 50.4 | 22.1 | 143 | | |
| electropolished | Surface roughness: Ra _{max} = 0.76 μm, optional order code for "Design", option CB: Ra _{max} = 0.38 μm electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs. | | | | | |


Couplings with O-ring seal available for order



| External th 1.4404 (31 Order code | | | | |
|---|--|--------------|-----------|-----------|
| DN [mm] | Suitable for internal thread NPT [in] | A [mm/in] | B [mm] | L [mm] |
| 2 to 8 | NPT 3/8 | R 15.5 × 3/8 | 10 | 186 |
| 15 | NPT ½ | R 20 × ½ | 16 | 186 |
| 25 | NPT 1 | R 25 × 1 | 25 | 196 |
| Surface rou | ighness: Ra _{may} = 1.6 µm | | | |

| Internal th 1.4404 (31 Order code | | | | |
|---|--|--------------|-----------|-----------|
| DN [mm] | Suitable for external thread NPT [in] | A [mm/in] | B [mm] | L [mm] |
| 2 to 8 | NPT 3/8 | R 13 × 3/8 | 8.9 | 176 |
| 15 | NPT ½ | R 14 × ½ | 16 | 176 |
| 25 | NPT 1 | R 17 × 1 | 27.2 | 188 |
| Surface rou | ghness: Ra _{max} = 1.6 μm | | | |

Grounding rings




For lap joint flange made of PVDF and PVC adhesive sleeve 1.4435 (316L), Alloy C22, tantalum Order code: DK5HR-****

| Officer could. D | Older Code, DKShik- | | | | | | | | | | | | |
|------------------|---------------------|------|------|------|------|------|------|------|------|--|--|--|--|
| DN | di | В | С | D | Е | F | G | Н | J | | | | |
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | | | | |
| 2 to 8 | 9 | 22 | 17.6 | 33.9 | 0.5 | 3.5 | 1.9 | 3.4 | 4.5 | | | | |
| 15 | 16 | 29 | 24.6 | 33.9 | 0.5 | 3.5 | 1.9 | 3.4 | 4.5 | | | | |
| 25 | 26 | 39 | 34.6 | 43.9 | 0.5 | 3.5 | 1.9 | 3.4 | 4.5 | | | | |

Dimensions in US units

Compact version



Order code for "Housing", option A "Aluminum, coated"

| DN | A 1) | B 1) | С | D | Е | F | G ²⁾ | Н | I ²⁾ | К | L ³⁾ | М |
|------------------------------|------|------|------|------|------|------|-----------------|------|-----------------|------|-----------------|------|
| [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] |
| ¹ / ₁₂ | 6.65 | 2.68 | 3.98 | 2.17 | 9.45 | 11.6 | 7.87 | 2.32 | 5.55 | 0.09 | 3.39 | 1.69 |
| 1/8 | 6.65 | 2.68 | 3.98 | 2.17 | 9.45 | 11.6 | 7.87 | 2.32 | 5.55 | 0.18 | 3.39 | 1.69 |
| 3/8 | 6.65 | 2.68 | 3.98 | 2.17 | 9.45 | 11.6 | 7.87 | 2.32 | 5.55 | 0.35 | 3.39 | 1.69 |
| 1/2 | 6.65 | 2.68 | 3.98 | 2.17 | 9.45 | 11.6 | 7.87 | 2.32 | 5.55 | 0.63 | 3.39 | 1.69 |
| 1 | 6.65 | 2.68 | 3.98 | 2.17 | 9.45 | 11.6 | 7.87 | 2.32 | 5.55 | 0.89 | 3.39 | 2.20 |

| DN | A 1) | B 1) | С | D | Е | F | G ²⁾ | Н | I ²⁾ | К | L ³⁾ | М |
|------|------|------|------|------|------|------|-----------------|------|-----------------|------|-----------------|------|
| [in] | [in] | [in] | [in] | [in] | [in] |
| 1 ½ | 6.65 | 2.68 | 3.98 | 2.13 | 9.41 | 11.5 | 7.87 | 2.32 | 5.55 | 1.37 | 5.51 | 4.21 |
| 2 | 6.65 | 2.68 | 3.98 | 2.36 | 9.69 | 12.1 | 7.87 | 2.32 | 5.55 | 1.87 | 5.51 | 4.72 |
| 3 | 6.65 | 2.68 | 3.98 | 2.91 | 10.2 | 13.2 | 7.87 | 2.32 | 5.55 | 2.87 | 5.51 | 5.83 |
| 4 | 6.65 | 2.68 | 3.98 | 3.43 | 10.8 | 14.2 | 7.87 | 2.32 | 5.55 | 3.83 | 5.51 | 6.85 |
| 6 | 6.65 | 2.68 | 3.98 | 4.61 | 11.9 | 16.5 | 7.87 | 2.32 | 5.55 | 5.78 | 7.87 | 9.21 |

1) Depending on the cable gland used: values up to + 1.18 in

2) For version without local display: values – 1.18 in

3) Total installed length depends on process connections. $\rightarrow \square 88$

| Order co | ode for " | Housing | ", option | ı A "Alur | ninum, | coated"; | Ex d | |
|----------|-----------|---------|-----------|-----------|--------|----------|------|---|
| | . 1) | - 1) | - | _ | _ | _ | - 21 | ĺ |

| DN | A 1) | B 1) | C | D | E | F | G 2) | H | I 2) | K | L ³⁾ | М |
|------|------|------|------|------|------|------|------|------|------|------|-----------------|------|
| [in] | [in] |
| 1/12 | 7.40 | 3.35 | 4.06 | 2.17 | 10.6 | 12.8 | 8.54 | 2.28 | 6.26 | 0.09 | 3.39 | 1.69 |
| 1/8 | 7.40 | 3.35 | 4.06 | 2.17 | 10.6 | 12.8 | 8.54 | 2.28 | 6.26 | 0.18 | 3.39 | 1.69 |
| 3⁄8 | 7.40 | 3.35 | 4.06 | 2.17 | 10.6 | 12.8 | 8.54 | 2.28 | 6.26 | 0.35 | 3.39 | 1.69 |
| 1/2 | 7.40 | 3.35 | 4.06 | 2.17 | 10.6 | 12.8 | 8.54 | 2.28 | 6.26 | 0.63 | 3.39 | 1.69 |
| 1 | 7.40 | 3.35 | 4.06 | 2.17 | 10.6 | 12.8 | 8.54 | 2.28 | 6.26 | 0.89 | 3.39 | 2.20 |
| 1 ½ | 7.40 | 3.35 | 4.06 | 2.13 | 10.6 | 12.8 | 8.54 | 2.28 | 6.26 | 1.37 | 5.51 | 4.21 |
| 2 | 7.40 | 3.35 | 4.06 | 2.36 | 10.9 | 13.2 | 8.54 | 2.28 | 6.26 | 1.87 | 5.51 | 4.72 |
| 3 | 7.40 | 3.35 | 4.06 | 2.91 | 11.4 | 14.3 | 8.54 | 2.28 | 6.26 | 2.87 | 5.51 | 5.83 |
| 4 | 7.40 | 3.35 | 4.06 | 3.43 | 11.9 | 15.4 | 8.54 | 2.28 | 6.26 | 3.83 | 5.51 | 6.85 |
| 6 | 7.40 | 3.35 | 4.06 | 4.61 | 13.1 | 17.7 | 8.54 | 2.28 | 6.26 | 5.78 | 7.87 | 9.21 |

Depending on the cable gland used: values up to + 1.18 in 1)

For version without local display: values – 1.57 in

2) 3) Total installed length depends on process connections. \rightarrow 🗎 88

Order code for "Housing", option B "Stainless, hygienic"


| DN | A 1) | B 1) | С | D | Е | F | G ²⁾ | Н | I ²⁾ | К | L ³⁾ | М |
|-------|------|------|------|------|------|------|-----------------|------|-----------------|------|-----------------|------|
| [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] |
| 1/12 | 7.20 | 2.87 | 4.33 | 2.17 | 10.0 | 12.2 | 8.15 | 2.56 | 5.59 | 0.09 | 3.39 | 1.69 |
| 1/8 | 7.20 | 2.87 | 4.33 | 2.17 | 10.0 | 12.2 | 8.15 | 2.56 | 5.59 | 0.18 | 3.39 | 1.69 |
| 3/8 | 7.20 | 2.87 | 4.33 | 2.17 | 10.0 | 12.2 | 8.15 | 2.56 | 5.59 | 0.35 | 3.39 | 1.69 |
| 1/2 | 7.20 | 2.87 | 4.33 | 2.17 | 10.0 | 12.2 | 8.15 | 2.56 | 5.59 | 0.63 | 3.39 | 1.69 |
| 1 | 7.20 | 2.87 | 4.33 | 2.17 | 10.0 | 12.2 | 8.15 | 2.56 | 5.59 | 0.89 | 3.39 | 2.20 |
| 1 1/2 | 7.20 | 2.87 | 4.33 | 2.13 | 10.0 | 12.2 | 8.15 | 2.56 | 5.59 | 1.37 | 5.51 | 4.21 |
| 2 | 7.20 | 2.87 | 4.33 | 2.63 | 10.3 | 12.6 | 8.15 | 2.56 | 5.59 | 1.87 | 5.51 | 4.72 |
| 3 | 7.20 | 2.87 | 4.33 | 2.91 | 10.8 | 13.7 | 8.15 | 2.56 | 5.59 | 2.87 | 5.51 | 5.83 |
| 4 | 7.20 | 2.87 | 4.33 | 3.43 | 11.3 | 14.8 | 8.15 | 2.56 | 5.59 | 3.83 | 5.51 | 6.85 |
| 6 | 7.20 | 2.87 | 4.33 | 4.61 | 12.5 | 17.1 | 8.15 | 2.56 | 5.59 | 5.78 | 7.87 | 9.21 |

1) Depending on the cable gland used: values up to + 1.18 in

For version without local display: values – 1.18 in 2)


3) Total installed length depends on process connections. \rightarrow 🗎 88

Sensor flange connection



| 🖻 51 | Front view without process connections |
|------|--|
|------|--|

| DN | А | В | С | D | E | F | G | Н | К | L | М |
|------|------|------|------|------|------|------|------|------|------|------|------|
| [in] | [mm] |
| 1/12 | 2.44 | 1.64 | 1.34 | 0.35 | 0.94 | 1.65 | 1.69 | 0.33 | 0.24 | 0.16 | M6 |
| 5/32 | 2.44 | 1.64 | 1.34 | 0.35 | 0.94 | 1.65 | 1.69 | 0.33 | 0.24 | 0.16 | M6 |
| 5/16 | 2.44 | 1.64 | 1.34 | 0.35 | 0.94 | 1.65 | 1.69 | 0.33 | 0.24 | 0.16 | M6 |
| 1/2 | 2.44 | 1.64 | 1.34 | 0.63 | 0.94 | 1.65 | 1.69 | 0.33 | 0.24 | 0.16 | M6 |
| 1 | 2.83 | 1.98 | 1.73 | 0.89 | 1.14 | 2.17 | 2.20 | 0.33 | 0.24 | 0.16 | M6 |




■ 52 Front view without process connections

| DN | А | В | С | D | E | F | G | Н | К | L |
|-------|------|------|------|------|------|------|------|------|-----------|-----------|
| | | | | | | | | | 90° ±0.5° | 60° ±0.5° |
| [in] | [in] | [in] | [in] | [in] | [in] | [mm] | [in] | [in] | Тарре | d holes |
| 1 1/2 | 3.93 | 3.38 | 2.80 | 1.90 | 1.37 | M8 | 0.47 | 0.67 | 4 | - |
| 2 | 4.44 | 3.89 | 3.29 | 2.37 | 1.87 | M8 | 0.47 | 0.67 | 4 | - |
| 3 | 5.54 | 5.26 | 4.49 | 3.50 | 2.87 | M8 | 0.47 | 0.67 | - | 6 |
| 4 | 6.56 | 6.28 | 5.55 | 4.50 | 3.83 | M8 | 0.47 | 0.67 | - | 6 |

| DN | А | В | С | D | E | F | G | Н | K | L |
|------|------|------|------|------|------|------|------|------|------------------|-----------|
| | | | | | | | | | 90° ±0.5° | 60° ±0.5° |
| [in] | [in] | [in] | [in] | [in] | [in] | [mm] | [in] | [in] | Тарре | l holes |
| 5 | 7.82 | 7.54 | 6.73 | 5.50 | 4.72 | M10 | 0.59 | 0.79 | - | 6 |
| 6 | 8.93 | 8.64 | 7.87 | 6.63 | 5.78 | M10 | 0.59 | 0.79 | - | 6 |


Flange connections

Flanges with O-ring seal



| Flange similar to ASME B16.5: Class 150 1.4404 (316L) Order code for "Process connection", option A1S | | | | | | | | | | | | |
|---|---|------|-----------|------|------|------|--|--|--|--|--|--|
| DN A B C D E L [in] [in] [in] [in] [in] [in] | | | | | | | | | | | | |
| ¹ / ₁₂ to ³ / ₈ ¹⁾ | 3.50 | 2.38 | 4 × Ø0.62 | 0.44 | 0.62 | 8.59 | | | | | | |
| 1/2 | 3.50 | 2.38 | 4 × Ø0.62 | 0.44 | 0.63 | 8.59 | | | | | | |
| 1 4.25 3.12 4 × Ø0.62 0.56 1.05 9.05 | | | | | | | | | | | | |
| Surface roughness: Ra _n | Surface roughness: Ra _{max} = 63 µin | | | | | | | | | | | |

1) DN $\frac{1}{12}$ to $\frac{3}{8}$ with DN $\frac{1}{2}$ " flanges as standard



| Lap joint flange s PVDF Order code for "Pro | | | | | | | |
|---|-----------|-----------|-----------------------|--------------|------------|-----------|-----------|
| DN [in] | A [in] | B [in] | C [in] | D [in] | E [in] | F [in] | L [in] |
| ¹ / ₁₂ to ³ / ₈ ¹⁾ | 3.74 | 2.36 | 4 × Ø 0.62 | 0.59 | 1.38 | 0.63 | 7.87 |
| 1/2 | 3.74 | 2.36 | 4 × Ø 0.62 | 0.59 | 1.38 | 0.63 | 7.87 |
| Surface roughness The required grou | | | ed as accessories (or | ler code: DK | 5HR-****). | • | |

The required grounding migs can be ordered as decessories (order code

1) DN $^{1}\!\!\!/_{12}$ to $^{3}\!\!/_{8}$ with DN $^{1}\!\!/_{2}$ "flanges as standard


| L ap joint flange sin P VDF Order code for "Proc | | | | | | | |
|---|-----------|-----------|------------|-----------|-----------|-----------|-----------|
| DN [in] | A [in] | B [in] | C [in] | D [in] | E [in] | F [in] | L [in] |
| ¹ / ₁₂ to ³ / ₈ ¹⁾ | 3.74 | 2.36 | 4 × Ø 0.62 | 0.59 | 1.38 | 0.63 | 7.87 |
| 1/2 | 3.74 | 2.36 | 4 × Ø 0.62 | 0.59 | 1.38 | 0.63 | 7.87 |

Grounding rings are not necessary.

1) DN $\frac{1}{12}$ to $\frac{3}{8}$ with DN $\frac{1}{2}$ " flanges as standard

Welding nipple

Welding nipple with aseptic gasket seal



| Welding nipple according to ISO 2037 1.4404 (316L), suitable for pipe ISO 2037 Order code for "Process connection", option IAS | | | | | | | |
|--|------------------------------------|-----------|-----------|-----------|--|--|--|
| DN [in] | Suitable for pipe ISO 2037 [in] | A [in] | B [in] | L [in] | | | |
| ¹ / ₁₂ to ³ / ₈ | 0.50 × 0.06 | 0.47 | 0.39 | 4.65 | | | |
| 1/2 | 0.75 × 0.06 | 0.71 | 0.63 | 4.65 | | | |
| 1 | 1.00×0.06 | 0.98 | 0.89 | 4.65 | | | |
| 1 1/2 | 1.50 × 0.05 | 1.50 | 1.40 | 8.66 | | | |
| 2 | 2.00 × 0.05 | 2.01 | 1.91 | 8.66 | | | |
| 3 | 3.00 × 0.06 | 3.00 | 2.87 | 8.66 | | | |
| 4 | 2.50 × 0.08 | 4.00 | 3.84 | 8.66 | | | |
| 5 | 4.00 × 0.08 | 5.50 | 5.34 | 15.00 | | | |

| 1.4404 (316L), sui | cording to ISO 2037 table for pipe ISO 2037 ess connection", option IAS | | | | |
|---|---|-----------|-----------|-----------|--|
| DN [in] | Suitable for pipe ISO 2037 [in] | A [in] | B [in] | L [in] | |
| 6 | 6.63 × 0.10 | 6.63 | 6.42 | 15.00 | |
| Surface reuchnesses Da = 21.5 uin entional order and for "Corrige" ention LII: Da = 1.5 uin electropolished | | | | | |

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.


Welding nipple according to ASME BPE

1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C Order code for "Process connection", option **AAS**

| DN [in] | Suitable for pipe according to ASME BPE [in] | A [in] | B [in] | L [in] |
|---|---|-----------|-----------|-----------|
| ¹ / ₁₂ to ³ / ₈ | 0.50 × 0.06 | 0.50 | 0.35 | 4.65 |
| 1/2 | 0.75 × 0.06 | 0.75 | 0.63 | 4.65 |
| 1 | 1.00 × 0.06 | 1.00 | 0.89 | 4.65 |
| 1 1/2 | 1.50 × 0.06 | 1.50 | 1.37 | 8.66 |
| 2 | 2.00 × 0.06 | 2.00 | 1.87 | 8.66 |
| 3 | 3.00 × 0.06 | 3.00 | 2.87 | 8.66 |
| 4 | 4.00 × 0.08 | 4.00 | 3.83 | 8.66 |
| 6 | 6.00 × 0.11 | 6.00 | 5.78 | 11.80 |

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.


Welding nipple with O-ring seal



| 1.4404 (316 | ple according to ISO 1127 L), suitable for pipe according to ISO 1127 series 1 r "Process connection", option A2S | | | |
|---|---|-----------|-----------|-----------|
| DN [in] | Suitable for pipe according to ISO 1127 series 1 [in] | A [in] | B [in] | L [in] |
| ¹ / ₁₂ to ³ / ₈ | 0.53 × 0.09 | 0.53 | 0.35 | 4.99 |
| 1/2 | 0.84 × 0.10 | 0.84 | 0.63 | 4.99 |
| Surface roug | hness: Ra _{max} = 63 μin | | | |

Clamp connections

Clamp connections with aseptic gasket seal



Tri-Clamp

1.4404 (316L), suitable for pipe according to ASME BPE and DIN 11866 series C Order code for "Process connection", option FAS

| DN [in] | Suitable for pipe according to ASME BPE [in] | A [in] | B [in] | L [in] |
|---|---|-----------|-----------|-----------|
| ¹ / ₁₂ to ³ / ₈ | 1/2 | 1 | 0.37 | 5.63 |
| 1/2 | 3⁄4 | 1 | 0.62 | 5.63 |
| 1 | 1 | 2 | 0.87 | 5.63 |
| 1 1/2 | 1.50 × 0.06 | 1.98 | 1.37 | 8.66 |
| 2 | 2.00 × 0.06 | 2.52 | 1.87 | 8.66 |
| 3 | 3.00 × 0.06 | 3.58 | 2.87 | 8.66 |
| 4 | 4.00 × 0.08 | 4.68 | 3.83 | 8.66 |
| 6 | 6.00 × 0.11 | 6.57 | 5.90 | 11.80 |
| | • | - | · | |


Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Clamp according to ISO 2852, Fig. 2 1.4404 (316L) Order code for "Process connection", option IBS DN Suitable for pipe ISO 2037 DN в Α L. [in] [in] Clamp ISO 2852 [in] [in] [in] [in] 0.89 6.87 1 0.96×0.06 1 2.00 1 1/2 1.50×0.06 1.50 1.99 1.40 8.66 2 2.00×0.06 2.01 2.52 1.91 8.66 3 3.00 2.87 3.00×0.06 3.58 8.66 3.84 4 2.50 × 0.08 4.00 4.69 8.66 5 4.00×0.08 5.50 5.34 11.80 6.10 6 6.63×0.10 6.63 7.20 6.42 11.80 Surface roughness: Ra_{max} = 31.5 µin, optional order code for "Service", option HJ: Ra_{max} = 15 µin electropolished

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Couplings

Thread with aseptic gasket seal



Coupling DIN 11851, thread

1.4404 (316L), suitable for pipe EN 10357 series B Order code for "Process connection", option **DCS**

| DN [in] | Suitable for pipe EN 10357 series B [in] | A [in] | B [in] | L [in] |
|--|---|---------------------------|-----------|-----------|
| ¹ / ₁₂ to ⁵ / ₁₆ | 0.47 × 0.04 (DN 1/8) | Rd 1.10 × 1/8 | 0.39 | 6.85 |
| 1/2 | 0.71 × 0.06 | Rd 1.34 × 1/8 | 0.63 | 6.85 |
| 1 | 1.10 × 0.04 or 1.10×0.06 | Rd 2.05 × 1/ ₆ | 1.02 | 7.48 |
| | | | | |

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling DIN 11851, thread

1.4404 (316L), suitable for pipe EN 10357 series A Order code for "Process connection", option **DCS**

| oracle code for Trocess connection, option Deb | | | | | | | |
|---|---|---------------------------------------|-----------|-----------|--|--|--|
| DN [in] | Suitable for pipe EN 10357 series A [in] | A [in] | B [in] | L [in] | | | |
| 1 1/2 | 1.65 × 0.06 | Rd 2.56 × ¹ / ₆ | 1.50 | 10.20 | | | |
| 2 | 2.13 × 0.06 | Rd 3.07 × 1/ ₆ | 1.97 | 10.20 | | | |
| 3 | 3.35 × 0.08 | Rd 4.33 × ¼ | 3.19 | 11.00 | | | |
| 4 | 4.09 × 0.08 | Rd 5.12× ¼ | 3.94 | 11.40 | | | |
| 5 | 5.08 × 0.08 | Rd 6.30 × ¼ | 4.92 | 15.00 | | | |
| 6 | 6.06 × 0.08 | Rd 6.30 × ¼ | 5.91 | 15.40 | | | |

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Coupling ISO 2853, thread 1.4404 (316L)

Order code for "Process connection", option ICS

| oraci e | | | | | | | | |
|------------|--|------------------------------|----------------|-----------|-----------|--|--|--|
| DN [in] | Suitable for pipe EN 10357 (DIN 11850) [in] | DN Clamp ISO 2853 [in] | A [in] | B [in] | L [in] | | | |
| 1 1/2 | 1.50 × 0.06 | 1.50 | Tr 2.00 × 0.13 | 1.40 | 10.80 | | | |
| 2 | 2.00 × 0.06 | 2.01 | Tr 2.52 × 0.13 | 1.91 | 10.80 | | | |
| 3 | 3.00 × 0.06 | 3.00 | Tr 3.58 × 0.13 | 2.87 | 10.90 | | | |
| 4 | 2.50 × 0.08 | 4.00 | Tr 4.65 × 0.13 | 3.84 | 11.30 | | | |
| | | | | _ | | | | |

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.


Coupling SMS 1145, thread 1.4404 (316L)

Order code for "Process connection", option SAS

| onder code for Trocess connection, option 5A5 | | | | | | | |
|---|---------------------------|------------------------|---------------------------|-----------|-----------|--|--|
| DN [in] | Suitable for pipe [in] | DN SMS 1145 [in] | A [in] | B [in] | L [in] | | |
| 1 | 1 | 1 | Rd1.57 × 0.17 | 0.89 | 5.81 | | |
| 1 1/2 | 1.50 × 0.06 | 1.50 | Rd 2.36 × ¼ | 1.37 | 10.10 | | |
| 2 | 2.00 × 0.06 | 2.00 | Rd 2.76 × ¼ | 1.87 | 10.10 | | |
| 3 | 3.00 × 0.06 | 3.00 | Rd 3.86 × ¼ | 2.86 | 10.90 | | |
| 4 | 4.00 × 0.08 | 4.00 | Rd 5.20 × 1/ ₆ | 3.83 | 11.30 | | |

Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Service", option HJ: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs.

Thread with O-ring seal




| 1.4404 (316) | ead according to ISO 228/DIN 2999 L) r "Process connection", option I2S | | | |
|---|---|--------------|-----------|-----------|
| DN [in] | Suitable for internal thread ISO 228/DIN 2999 [in] | A [in] | B [in] | L [in] |
| ¹ / ₁₂ to ³ / ₈ | R 3/8 | R 0.40 × 3/8 | 0.39 | 6.53 |
| 1/2 | R 1⁄2 | R 0.52 × ½ | 0.63 | 6.53 |
| 1 | R 1 | R 0.66 × 1 | 0.98 | 6.69 |

Surface roughness: $Ra_{max} = 63 \ \mu in$

| Internal thread according to ISO 228/DIN 2999 1.4404 (316L) Order code for "Process connection", option I3S | | | | | | |
|---|---|-------------|-----------|-----------|--|--|
| DN [in] | Suitable for external thread ISO 228/DIN 2999 [in] | A [in] | B [in] | L [in] | | |
| ¹ / ₁₂ to ³ / ₈ | Rp ¾ | Rp 0.51 × ¾ | 0.35 | 6.93 | | |
| 1/2 | Rp ½ | Rp 0.55 × ½ | 0.63 | 6.93 | | |
| 1 | Rp 1 | Rp 0.67 × 1 | 1.07 | 7.41 | | |
| Surface roug | Jhness: Ra _{max} = 63 μin | | | | | |

Adhesive sleeves


Adhesive sleeves with O-ring seal



| Adhesive sleeve PVC Order code for "Process connection", option O1V | | | | | | |
|---|---|-----------|-----------|-----------|-----------|-----------|
| DN [in] | Suitable for pipe [in] | A [in] | B [in] | C [in] | D [in] | L [in] |
| ¹ / ₁₂ to ³ / ₈ | 1/2 | 2.44 | 1.52 | 0.71 | 0.85 | 6.42 |
| | Surface roughness: Ra _{max} = 63 µin The required grounding rings can be ordered as accessories (order code: DK5HR-****). | | | | | |

Mounting kits


Wall mounting kit



| А | В | С | Ø D | Е | F |
|------|------|------|------|------|------|
| [in] | [in] | [in] | [in] | [in] | [in] |
| 5.39 | 4.33 | 4.72 | 0.28 | 4.92 | 3.46 |


Accessories

Weather protection cover





Remote display and operating module DKX001




🛃 54 Engineering unit mm (in)

External WLAN antenna



The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



E 55 Engineering unit mm (in)


External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/ reception conditions at the transmitter mounting location are poor.




☑ 56 Engineering unit mm (in)


Spacer



| Order code: DK5HB-**** | | | | | | |
|------------------------|------|------|------|------|--|--|
| DN | di | D1 | D2 | L | | |
| [in] | [in] | [in] | [in] | [in] | | |
| 3 | 2.87 | 5.54 | 5.55 | 1.30 | | |
| 4 | 3.83 | 6.56 | 6.38 | 1.30 | | |








Tri-Clamp

1.4404 (316L), suitable for pipe according to ASME BPE and BS 4825, reduction from pipe OD 1" (Tri-Clamp connection) to device DN 15 Order code: DKH**-HF**

| DN [in] | Suitable for pipe according to ASME BPE and BS 4825 (reduction) [in] | A [in] | B [in] | L [in] | | | |
|------------|--|-----------|-----------|-----------|--|--|--|
| 1/2 | Pipe OD 1" | 2 | 0.87 | 5.63 | | | |
| | Surface roughness: $Ra_{max} = 31.5 \mu in$, optional order code for "Design", option CB: $Ra_{max} = 15 \mu in$ electropolished Please note the internal diameters of the measuring pipe and process connection (B) when cleaning with pigs. | | | | | | |


Couplings with O-ring seal available for order



| External three 1.4404 (316L Order code: D |) | | | |
|---|--|--------------|-----------|-----------|
| DN [in] | Suitable for internal thread NPT [in] | A [in] | B [in] | L [in] |
| ¹ / ₁₂ to ³ / ₈ | NPT 3/8 | R 0.61 × 3/8 | 0.39 | 7.39 |
| 1/2 | NPT ½ | R 0.79 × ½ | 0.63 | 7.39 |
| 1 | NPT 1 | R 1 × 1 | 1.00 | 7.73 |
| Surface rough | ness: Ra _{max} = 63 μin | | | |

| Internal threa 1.4404 (316L Order code: D |) | | | |
|---|--|--------------|-----------|-----------|
| DN [in] | Suitable for external thread NPT [in] | A [in] | B [in] | L [in] |
| ¹ / ₁₂ to ³ / ₈ | NPT 3/8 | R 0.51 × 3/8 | 0.35 | 6.93 |
| 1/2 | NPT ½ | R 0.55 × ½ | 0.63 | 6.93 |
| 1 | NPT 1 | R 0.67 × 1 | 1.07 | 7.41 |
| Surface rough | ness: Ra _{max} = 63 μin | | | |

Grounding rings



| For lap joint flange 1.4435 (316L), Allo Order code: DK5HR | y C22, tantalu | | esive sleeve | | | | | | |
|--|----------------|------|--------------|------|------|------|------|------|------|
| DN | di | В | С | D | E | F | G | Н | J |
| [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] |
| ¹ / ₁₂ to ³ / ₈ | 0.35 | 0.87 | 0.69 | 1.33 | 0.02 | 0.14 | 0.07 | 0.13 | 0.18 |
| 1/2 | 0.63 | 1.14 | 0.97 | 1.33 | 0.02 | 0.14 | 0.07 | 0.13 | 0.18 |
| 1 | 0.89 | 1.44 | 1.23 | 1.73 | 0.02 | 0.14 | 0.07 | 0.13 | 0.18 |

Weight

All values (weight exclusive of packaging material) refer to devices with flanges of the standard pressure rating.

The weight may be lower than indicated depending on the pressure rating and design. Weight specifications including transmitter as per order code for "Housing", option A "Aluminum, coated".

Different values due to different transmitter versions:

- Transmitter version for the hazardous area
- (Order code for "Housing", option A "Aluminum, coated"; Ex d): +2 kg (+4.4 lbs)
- Transmitter version for hygienic area (Order code for "Housing", option B "Stainless, hygienic"): +0.2 kg (+0.44 lbs)

| Nominal | diameter | Weight | | |
|---------|----------|--------|-------|--|
| [mm] | [in] | [kg] | [lbs] | |
| 2 | 1/12 | 4.7 | 10.4 | |
| 4 | 5/32 | 4.7 | 10.4 | |
| 8 | 5/16 | 4.7 | 10.4 | |
| 15 | 1/2 | 4.6 | 10.1 | |

| Nominal | diameter | Weight | | |
|---------|----------|--------|-------|--|
| [mm] | [in] | [kg] | [lbs] | |
| 25 | 1 | 5.5 | 12.1 | |
| 40 | 1 ½ | 6.8 | 15.0 | |
| 50 | 2 | 7.3 | 16.1 | |
| 65 | - | 8.1 | 17.9 | |
| 80 | 3 | 8.7 | 19.2 | |
| 100 | 4 | 10.0 | 22.1 | |
| 125 | 5 | 15.4 | 34.0 | |
| 150 | 6 | 17.8 | 39.3 | |

Measuring tube specification

| Nominal | diameter | Pressure rating ¹⁾ | Process connection | internal diameter | |
|---------|----------|-------------------------------|--------------------|--------------------|--|
| | | EN (DIN) | PFA | | |
| [mm] | [in] | [bar] | [mm] | [in] | |
| 2 | 1/12 | PN 16/40 | 2.25 | 0.09 | |
| 4 | 5/32 | PN 16/40 | 4.5 | 0.18 | |
| 8 | 5/16 | PN 16/40 | 9.0 | 0.35 | |
| 15 | 1/2 | PN 16/40 | 16.0 | 0.63 | |
| _ | 1 | PN 16/40 | 22.6 ²⁾ | 0.89 ²⁾ | |
| 25 | - | PN 16/40 | 26.0 ³⁾ | 1.02 ³⁾ | |
| 40 | 1 ½ | PN 16/25/40 | 35.3 | 1.39 | |
| 50 | 2 | PN 16/25 | 48.1 | 1.89 | |
| 65 | - | PN 16/25 | 59.9 | 2.36 | |
| 80 | 3 | PN 16/25 | 72.6 | 2.86 | |
| 100 | 4 | PN 16/25 | 97.5 | 3.84 | |
| 125 | 5 | PN 10/16 | 120.0 | 4.72 | |
| 150 | 6 | PN 10/16 | 146.5 | 5.77 | |

1) Depending on process connection and seals used

2) Order code 5H**22

3) Order code 5H**26

Materials

Transmitter housing

Order code for "Housing":

- Option A "Aluminum, coated": aluminum, AlSi10Mg, coated
- Option **B** "Stainless, hygienic": stainless steel, 1.4404 (316L)

Window material


Order code for "Housing":

- Option **A** "Aluminum, coated": glass
- Option **B** "Stainless, hygienic": polycarbonate

Seals

Order code for "Housing": Option **B** "Stainless, hygienic": EPDM and silicone

Cable entries/cable glands



■ 58 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland $M20 \times 1.5$
- 3 Adapter for cable entry with female thread G ¹/₂" or NPT ¹/₂"
- 4 Device plug

Order code for "Housing", option A "Aluminum, coated"

The various cable entries are suitable for hazardous and non-hazardous areas.

| Cable entry/cable gland | Material |
|--|-------------------------------------|
| Compression fitting M20 × 1.5 | Non-Ex: plastic |
| Compression fitting M20 × 1.5 | Z2, D2, Ex d/de: brass with plastic |
| Adapter for cable entry with female thread G ½" | Nickel-plated brass |
| Adapter for cable entry with female thread NPT $\frac{1}{2}$ " | |

Order code for "Housing", option B "Stainless, hygienic"

The various cable entries are suitable for hazardous and non-hazardous areas.

| Cable entry/cable gland | Material |
|--|---------------------|
| Cable gland M20 × 1.5 | Plastic |
| Adapter for cable entry with female thread G $^{1\!\!/}_{2"}$ | Nickel-plated brass |
| Adapter for cable entry with female thread NPT $\frac{1}{2}$ " | |

Device plug

| Electrical connection | Material |
|-----------------------|---|
| Plug M12x1 | Socket: Stainless steel, 1.4404 (316L) Contact housing: Polyamide Contacts: Gold-plated brass |

Sensor housing

Stainless steel 1.4301 (304)

Measuring tubes

Stainless steel 1.4301 (304)

Liner

PFA (USP Class VI, FDA 21 CFR 177.2600)

Process connections

- Stainless steel, 1.4404 (F316L)
- PVDF
- PVC adhesive sleeve

Electrodes

Standard: 1.4435 (316L)

Seals

- O-ring seal, DN 2 to 25 (1/12 to 1"): EPDM, FKM ²⁾, Kalrez
- Aseptic³⁾ gasket seal, DN 2 to 150 (1/12 to 6"): EPDM, FKM²⁾, VMQ (silicone)

Accessories

Protective cover

Stainless steel, 1.4404 (316L)

External WLAN antenna

- Antenna: ASA plastic (acrylonitrile styrene acrylate) and nickel-plated brass
- Adapter: Stainless steel and nickel-plated brass
- Cable: Polyethylene
- Plug: Nickel-plated brass
- Angle bracket: Stainless steel

Grounding rings

- Standard: 1.4435 (316L)
- Optional: Alloy C22, tantalum

Wall mounting kit

Stainless steel, 1.4301 (304) 4)

Centering star

1.4435 (F316L)

| Fitted electrodes | 2 measuring electrodes for signal detection 1 empty pipe detection electrode for empty pipe detection/temperature measurement (only DN 19 to 150 (1/2 to 6")) | |
|---------------------|--|--|
| Process connections | With O-ring seal: • Welding nipple (DIN EN ISO 1127, ODT/SMS, ISO 2037) • Flange (EN (DIN), ASME, JIS) • Flange from PVDF (EN (DIN), ASME, JIS) • Male thread • Female thread • Hose connection • PVC adhesive sleeve | |
| | With aseptic gasket seal: Coupling (DIN 11851, DIN 11864-1, ISO 2853, SMS 1145) Flange DIN 11864-2 | |
| | For information on the different materials used in the process connections $\rightarrow \square$ 101 | |
| Surface roughness | Electrodes: ■ Stainless steel, 1.4435 (316L) electropolished ≤ 0.5 μm (19.7 μin) ■ Alloy C22, 2.4602 (UNSN06022); tantalum ≤ 0.5 μm (19.7 μin) | |

2) USP Class VI, FDA 21 CFR 177.2600, 3A

³⁾ In this context, aseptic means hygienic design

⁴⁾ Does not meet the hygienic design installation guidelines.

(All data refer to parts in contact with the medium)

Liner with PFA: $\leq 0.4 \ \mu m$ (15.7 μin)

(All data refer to parts in contact with the medium)

Stainless steel process connections:

- With O-ring seal: $\leq 1.6 \ \mu m \ (63 \ \mu in)$
- With aseptic seal: $Ra_{max} = 0.76 \ \mu m (31.5 \ \mu in)$ Optional: $Ra_{max} = 0.38 \ \mu m (15 \ \mu in)$ electropolished

(All data refer to parts in contact with the medium)

| | Operability | | | |
|-------------------|---|--|--|--|
| Operation concept | Operator-oriented menu structure for user-specific tasks Commissioning Operation Diagnosis Expert level | | | |
| | Quick and safe commissioning Guided menus ("Make-it-run" wizards) for applications Menu guidance with brief descriptions of the individual parameter functions Access to the device via web server WLAN access to the device via mobile handheld terminal, tablet or smart phone | | | |
| | Reliable operation Operation in local language Uniform operating philosophy applied to device and operating tools If replacing electronic modules, transfer the device configuration via the integrated memory (HistoROM backup) which contains the process and measuring device data and the event logbook No need to reconfigure. | | | |
| | Efficient diagnostics increase measurement reliability Troubleshooting measures can be called up via the device and in the operating tools Diverse simulation options, logbook for events that occur and optional line recorder functions | | | |
| Languages | Can be operated in the following languages: Via local operation English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Korean, Vietnamese, Czech, Swedish Via web browser English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Vietnamese, Czech, Swedish Via "FieldCare", "DeviceCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese | | | |
| Onsite operation | Via display module | | | |
| | Features: Order code for "Display; operation", option F "4-line, illuminated, graphic display; touch control" Order code for "Display; operation", option G "4-line, illuminated, graphic display; touch control + WLAN" Information about WLAN interface → 111 | | | |
| | ■ Image: Solution with touch control | | | |
| | Display elements | | | |

- 4-line, illuminated, graphic display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured

Operating elements

- External operation via touch control (3 optical keys) without opening the housing:


 □, □, □

 Operating elements also accessible in the various zones of the hazardous area

Via remote display and operating module DKX001

The remote display and operating module DKX001 is available as an optional extra ightarrow [ightarrow 121...

- The remote display and operating module DKX001 is only available for the following housing version: order code for "Housing": option A "Aluminum, coated"
- The measuring instrument is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring instrument. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring instrument display module. Only one display or operation unit may be connected to the transmitter at any one time.



60 Operation via remote display and operating module DKX001

Display and operating elements

The display and operating elements correspond to those of the display module $\rightarrow \square$ 103.

Housing material

-

The housing material of the display and operating module DKX001 corresponds to the selected material of the transmitter housing.

| Transmitter housing | | Remote display and operating module |
|------------------------------------|------------------|-------------------------------------|
| Order code for "Housing" | Material | Material |
| Option A "Aluminum, coated" | AlSi10Mg, coated | AlSi10Mg, coated |

Cable entry

Corresponds to the choice of transmitter housing, order code for "Electrical connection".

Connecting cable

→ 🗎 50


Dimensions

→ 🗎 82

Remote operation


Via HART protocol

This communication interface is available in device versions with a HART output.



61 Options for remote operation via HART protocol (active)

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 Field Xpert SMT70
- 7 VIATOR Bluetooth modem with connecting cable
- 8 Transmitter




62 Options for remote operation via HART protocol (passive)

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 Field Xpert SMT70
- 9 VIATOR Bluetooth modem with connecting cable
- 10 Transmitter

Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




63 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- 3 Industry network
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device

Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




64 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Measuring device

Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.




■ 65 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Segment coupler PROFIBUS DP/PA
- 5 PROFIBUS PA network
- 6 T-box
- 7 Measuring device

Via Modbus RS485 protocol

This communication interface is available in device versions with a Modbus RS485 output.



66 Options for remote operation via Modbus RS485 protocol (active)


1 Control system (e.g. PLC)

- 2 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 3 Transmitter

Via EtherNet/IP network

This communication interface is available in device versions with EtherNet/IP.

Star topology




67 Options for remote operation via EtherNet/IP network: star topology

- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 5 Measuring device

Ring topology

The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).




68 Options for remote operation via EtherNet/IP network: ring topology

- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 5 Measuring device

Via PROFINET network

This communication interface is available in device versions with PROFINET.

Star topology




69 Options for remote operation via PROFINET network: star topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
 2 Standard Ethermateuristic as a Scalares X204 (Cimerus)
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Ring topology


The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).



☑ 70 Options for remote operation via PROFINET network: ring topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Via APL network



■ 71 Options for remote operation via APL network

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch, e.g. Scalance X204 (Siemens)
- Computer with Web browser (e.g. Internet Explorer) for access to integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare with PROFINET COM DTM or SIMATIC PDM with FDI-Package)
 APL power switch (optional)
- 5 APL field switch
- 6 Measuring device

1

Service interface


Via service interface (CDI-RJ45)

A point-to-point connection can be established to configure the device onsite. With the housing open, the connection is established directly via the service interface (CDI-RJ45) of the device.

An adapter for the RJ45 to the M12 plug is optionally available for the non-hazardous area:

Order code for "Accessories", option **NB**: "Adapter RJ45 M12 (service interface)"


The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can be established via an M12 plug without opening the device.



- 72 Connection via service interface (CDI-RJ45)
- 1 Computer with web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated web server or with "FieldCare" operating tool, "DeviceCare" with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 2 Standard Ethernet connecting cable with RJ45 plug
- 3 Service interface (CDI-RJ45) of the measuring device with access to the integrated Web server

Via WLAN interface

The optional WLAN interface is available on the following device version: Order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN"



- 1 Transmitter with integrated WLAN antenna
- 2 Transmitter with external WLAN antenna
- 3 LED lit constantly: WLAN reception is enabled on measuring device
- 4 LED flashing: WLAN connection established between operating unit and measuring device
- 5 Computer with WLAN interface and web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device web server or with operating tool (e.g. FieldCare, DeviceCare)
- 6 Mobile handheld terminal with WLAN interface and web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device web server or operating tool (e.g. FieldCare, DeviceCare)
- 7 Smart phone or tablet (e.g. Field Xpert SMT70)

| Function | WLAN: IEEE 802.11 b/g (2.4 GHz) • Access Point with DHCP server (factory setting) • Network |
|------------------------------|---|
| Encryption | WPA2-PSK AES-128 (in accordance with IEEE 802.11i) |
| Configurable WLAN channels | 1 to 11 |
| Degree of protection | IP67 |
| Available antennas | Internal antenna External antenna (optional) In the event of poor transmission/reception conditions at the place of installation. Available as an accessory → |
| Range | Internal antenna: typically 10 m (32 ft) External antenna: typically 50 m (164 ft) |
| Materials (external antenna) | Antenna: ASA plastic (acrylonitrile styrene acrylate) and nickel-plated brass Adapter: Stainless steel and nickel-plated brass Cable: Polyethylene Plug: Nickel-plated brass Angle bracket: Stainless steel |


Network integration

Network integration is only available for the HART communication protocol.

With the optional "OPC-UA Server" application package, the device can be integrated into an Ethernet network via the service interface (CDI-RJ45 and WLAN) and communicate with OPC-UA clients. If the device is used in this way, IT security must be considered.



Transmitters with an Ex de approval may **not** be connected via the service interface (CDI-RJ45)! Order code for "Approval transmitter + sensor", options (Ex de): BB, C2, GB, MB, NB For permanent access to device data and for device configuration via the Web server, the device is incorporated directly in a network via the service interface (CDI-RJ45). In this way, the device can be accessed any time from the control station. The measured values are processed separately via the inputs and outputs through the automation system.



Supported operating tools

Different operating tools can be used for local or remote access to the measuring device. Depending on the operating tool used, access is possible with different operating units and via a variety of interfaces.

| Supported operating tools | Operating unit | Interface | Additional information |
|---------------------------|--|---|----------------------------------|
| Web browser | Notebook, PC or tablet with Web browser | CDI-RJ45 service interface WLAN interface Ethernet-based fieldbus (EtherNet/IP, PROFINET) | Special Documentation for device |
| DeviceCare SFE100 | Notebook, PC or tablet with Microsoft Windows system | CDI-RJ45 service interface WLAN interface Fieldbus protocol | → ● 123 |
| FieldCare SFE500 | Notebook, PC or tablet with Microsoft Windows system | CDI-RJ45 service interface WLAN interface Fieldbus protocol | → ➡ 123 |

| Supported operating tools | Operating unit | Interface | Additional information |
|---------------------------|---|---|--|
| Field Xpert | SMT70/77/50 | All fieldbus protocols WLAN interface Bluetooth CDI-RJ45 service interface | Operating Instructions BA01202S Device description files: Use update function of handheld terminal |
| SmartBlue app | Smartphone or tablet with iOs or Android | WLAN | → 🗎 123 |

Other operating tools based on FDT technology with a device driver such as DTM/iDTM or DD/EDD can be used for device operation. These operating tools are available from the individual manufacturers. Integration into the following operating tools, among others, is supported:

- FactoryTalk AssetCentre (FTAC) from Rockwell Automation → www.rockwellautomation.com
- Process Device Manager (PDM) from Siemens → www.siemens.com
- Asset Management Solutions (AMS) from Emerson → www.emersonprocess.com
- FieldCommunicator 375/475 from Emerson → www.emersonprocess.com
- Field Device Manager (FDM) from Honeywell → www.process.honeywell.com
- FieldMate from Yokogawa → www.yokogawa.com
- PACTWare → www.pactware.com

The related device description files are available: www.endress.com \rightarrow Download Area

Web server

With the integrated web server, the device can be operated and configured via a web browser using Ethernet-APL, and via the service interface (CDI-RJ45) or WLAN interface. The structure of the operating menu is the same as for the local display. In addition to the measured values, status information on the device is displayed and can be used to monitor device health. Furthermore the device data can be managed and the network parameters can be configured.

Access to the network is required for the Ethernet-APL connection.

A device that has a WLAN interface (can be ordered as an option) is required for the WLAN connection: order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN". The device acts as an Access Point and enables communication by computer or a mobile handheld terminal.

Supported functions

Data exchange between the operating unit (such as a notebook, for example,) and measuring device:

- Upload the configuration from the measuring device (XML format, configuration backup)
- Save the configuration to the measuring device (XML format, restore configuration)
- Export event list (.csv file)
- Export parameter settings (.csv file or PDF file, document the measuring point configuration)
- Export the Heartbeat verification report (PDF file, only available with the **Heartbeat Verification** $\rightarrow \cong 120$ application package)
- Flash firmware version for device firmware upgrade, for example
- Download driver for system integration
- Visualize up to 1000 saved measured values (only available with the Extended HistoROM application package →
 ^(a) 120)

HistoROM data management

agement The measuring device features HistoROM data management. HistoROM data management comprises both the storage and import/export of key device and process data, making operation and servicing far more reliable, secure and efficient.



When the device is delivered, the factory settings of the configuration data are stored as a backup in the device memory. This memory can be overwritten with an updated data record, for example after commissioning.

Additional information on the data storage concept

There are different types of data storage units in which device data are stored and used by the device:

| | HistoROM backup | T-DAT | S-DAT |
|------------------|--|--|---|
| Available data | Event logbook, e.g. diagnostic events Parameter data record backup Device firmware package Driver for system integration for exporting via web server, e.g.: GSD for PROFIBUS DP GSD for PROFIBUS PA GSDML for PROFINET EDS for EtherNet/IP DD for FOUNDATION Fieldbus | Measured value logging ("Extended HistoROM" order option) Current parameter data record (used by firmware at run time) Indicator (minimum/maximum values) Totalizer value | Sensor data: e.g. nominal diameter Serial number Calibration data Device configuration (e.g. SW options, fixed I/O or multi I/O) |
| Storage location | Fixed on the user interface PC board in the connection compartment | Can be plugged into the user interface PC board in the connection compartment | In the sensor plug in the transmitter neck part |

Data backup

Automatic

- The most important device data (sensor and transmitter) are automatically saved in the DAT modules
- If the transmitter or measuring device is replaced: once the T-DAT containing the previous device data has been exchanged, the new measuring device is ready for operation again immediately without any errors
- If exchanging the electronics module (e.g. I/O electronics module): Once the electronics module has been replaced, the software of the module is compared against the current device firmware. The module software is upgraded or downgraded where necessary. The electronics module is available for use immediately afterwards and no compatibility problems occur.

Manual

Additional parameter data record (complete parameter settings) in the integrated device memory HistoROM backup for:

- Data backup function
- Backup and subsequent restoration of a device configuration in the device memory HistoROM backup
- Data comparison function

Comparison of the current device configuration with the device configuration saved in the device memory HistoROM backup

Data transmission

Manual

- Transfer of a device configuration to another device using the export function of the specific operating tool, e.g. with FieldCare, DeviceCare or Web server: to duplicate the configuration or to store in an archive (e.g. for backup purposes)
- Transmission of the drivers for system integration via Web server, e.g.:
 - GSD for PROFIBUS DP
 - GSD for PROFIBUS PA
 - GSDML for PROFINET
 - EDS for EtherNet/IP
 - DD for FOUNDATION Fieldbus

Event list

Automatic

- Chronological display of up to 20 event messages in the events list
- If the **Extended HistoROM** application package (order option) is enabled: up to 100 event messages are displayed in the events list along with a time stamp, plain text description and remedial measures
- The events list can be exported and displayed via a variety of interfaces and operating tools e.g. DeviceCare, FieldCare or Web server

| | Data logging | | |
|--------------|---|--|--|
| | Manual If the Extended HistoROM application package | neasured values (up to 250 measured values per | |
| | Certificates and approvals | | |
| | Current certificates and approvals for the product are available at www.endress.com on the relevant product page: | | |
| | 1. Select the product using the filters and search field. | | |
| | 2. Open the product page. | | |
| | 3. Select Downloads . | | |
| CE mark | The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied. | | |
| | Endress+Hauser confirms successful testing of the device by affixing to it the CE mark. | | |
| UKCA marking | The device meets the legal requirements of the applicable UK regulations (Statutory Instruments). These are listed in the UKCA Declaration of Conformity along with the designated standards. By selecting the order option for UKCA marking, Endress+Hauser confirms a successful evaluation and testing of the device by affixing the UKCA mark. Contact address Endress+Hauser UK: Endress+Hauser Ltd. Floats Road Manchester M23 9NF United Kingdom www.uk.endress.com | | |
| RCM marking | The measuring system meets the EMC requirements of the "Australian Communications and Med Authority (ACMA)". | | |
| Ex approval | The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate. | | |
| | The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center. | | |
| | ATEX, IECEx | | |
| | Currently, the following versions for use in hazardous areas are available: | | |
| | Currently, the following versions for use in haza | ardous areas are available: | |
| | Currently, the following versions for use in haza | ardous areas are available: | |
| | | ardous areas are available: Type of protection | |

| Category | Type of protection |
|----------|--------------------|
| II2D | Ex tb IIIC Txxx Db |

Ех ес

| Category | Type of protection |
|----------|----------------------|
| II3G | Ex ec ic IIC T5T1 Gc |

cCSAus

Currently, the following versions for use in hazardous areas are available:

IS (Ex i) and XP (Ex d) Class I, II, III Division 1 Groups A-G

NI (Ex nA)

Class I Division 2 Groups A - D

Ex de

Class I, Zone 1 AEx/ Ex de ia IIC T6...T1 Gb

Ex nA

Class I, Zone 2 AEx/Ex nA ic IIC T5...T1 Gc

Ex tb

Zone 21 AEx/ Ex tb IIIC T** °C Db

| Sanitary compatibility | 3-A SSI 28-06 or more recent Confirmation by affixing the 3-A logo for measuring devices with the order code for "Additional approval", option LP "3-A". The 3-A approval refers to the measuring device. When installing the measuring device, ensure that no liquid can accumulate on the outside of the measuring device. Remote transmitters must be installed in accordance with the 3-A Standard. Accessories (e.g. weather protection cover, wall holder unit) must be installed in accordance with the 3-A Standard. Each accessory can be cleaned. Disassembly may be necessary under certain circumstances. EHEDG Type EL Class I Confirmation by affixing the EHEDG symbol for measuring devices with the order code for "Additional approval", option LT "EHEDG". |
|------------------------------|---|
| | EPDM is not a suitable seal material for fluids with a fat content > 8 %. To meet the requirements for EHEDG certification, the device must be used with process connections in accordance with the EHEDG position paper entitled "Easy Cleanable Pipe Couplings and Process Connections" (www.ehedg.org). FDA 21 CFR 177 Food Contact Materials Regulation (EC) 1935/2004 Food Contact Materials Regulation China GB 4806 Pasteurized Milk Ordinance (PMO) |
| Pharmaceutical compatibility | FDA 21 CFR 177 USP <87> USP <88> Class VI 121 °C TSE/BSE Certificate of Suitability cGMP Devices with the order code for "Test, certificate", option JG "Conformity with cGMP-derived requirements, declaration" comply with the requirements of cGMP with regard to the surfaces of parts in contact with the medium, design, FDA 21 CFR material conformity, USP Class VI tests and TSE/BSE conformity. A serial number-specific declaration is generated. |
| Functional safety | The measuring instrument can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture; order code for "Additional approval", option LA) and SIL 3 (multi- channel architecture with homogeneous redundancy) and is independently evaluated and certified i accordance with IEC 61508. The following types of monitoring in safety-related systems are possible: |

Restrictions

- Valid single gases:
 - Air
 - Methane (CH₄)
 - Carbon dioxide CO_2
- Nitrogen (N₂)
- Oxygen (O₂)
- Valid 4-component natural gas composition in mol%:
- CH₄ 80 to 99 %
- N₂ 0.3 to 12 %
- C₂H₆ 0.3 to 12 %
- CO₂ 0.3 to 12 %
- Extended natural gas range I: The listed 4-component natural gas composition may be extended by a selection of the following components up to a maximum proportion according to the following table:

| Additional natural gas components | Max. mol% |
|---|-----------|
| Propane (C ₃ H ₈) | 2 % |
| Butane (i-C ₄ H ₁₀ , n-C ₄ H ₁₀) | 1 % |
| Pentane (i- C_5H_{12} , n- C_5H_{12}) | 0.2 % |
| Hexane (i- C_6H_{14} , n- C_6H_{14}) | 0.2 % |
| Oxygen (O ₂) | 0.2 % |

- Extended natural gas range II: Natural gas mixtures that correspond to the 4-component natural gas composition or extended natural gas range I, with CO₂ and/or N₂ proportions of less than 0.3 mol% each (as defined in the 4-component mixture) are possible, taking into account the special configuration instructions in "Configuring the extended natural gas range".
- Temperature range: -30 to +150 °C (-22 to +302 °F)
- Pressure range: 0.8 to 30 bar (11.6 to 435 psi)
- Nominal diameters: Up to 320 mm (12.6 in) internal diameter
- Circular pipe for insertion version (cannot be used in rectangular ducts)
- The maximum flow rate during operation must not exceed the specified calibrated maximum value for the sensor.
- Measurement uncertainty in the SIL mode (see "Guidelines for minimum measurement error" in the Special Documentation for Functional Safety).

Functional safety manual with information for the SIL device $\rightarrow \square 124$

| HART certification | HART interface |
|------------------------|---|
| | The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications: Certified according to HART 7 The device can also be operated with certified devices of other manufacturers (interoperability) |
| FOUNDATION Fieldbus | FOUNDATION Fieldbus interface |
| certification | The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications: Certified in accordance with FOUNDATION Fieldbus H1 Interoperability Test Kit (ITK), revision version 6.2.0 (certificate available on request) Physical Layer Conformance Test The device can also be operated with certified devices of other manufacturers (interoperability) |
| Certification PROFIBUS | PROFIBUS interface |
| | The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V./ PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications: Certified according to PA Profile 3.02 The device can also be operated with certified devices of other manufacturers (interoperability) |

| EtherNet/IP certification | The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications: Certified in accordance with the ODVA Conformance Test EtherNet/IP Performance Test EtherNet/IP PlugFest compliance The device can also be operated with certified devices of other manufacturers (interoperability) |
|---------------------------------|---|
| Certification PROFINET | PROFINET interface |
| | The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V. / PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications: Certified according to: Test specification for PROFINET devices PROFINET Security Level 2 – Netload Class 2 0 Mbps The device can also be operated with certified devices of other manufacturers (interoperability) The device supports PROFINET S2 system redundancy. |
| PROFINET with Ethernet- | PROFINET interface |
| APL certification | The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e. V./ PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications: Certified according to: Test specification for PROFINET devices PROFINET PA Profile 4 PROFINET netload robustness Class 2 10 Mbit/s APL conformance test The device can also be operated with certified devices of other manufacturers (interoperability) The device supports PROFINET S2 system redundancy. |
| Radio approval | The measuring device has radio approval. |
| | For detailed information on the radio approval, see the Special Documentation |
| Pressure Equipment Directive | The measuring devices can be ordered with or without PED or PESR. If a device with PED or PESR is required, this must be ordered explicitly. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary. A UK order option must be selected for PESR under the order code for "Approvals". |
| | With the marking |
| | a) $PED/G1/x$ (x = category) or b) $PESR/G1/x$ (x = category) |
| | on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements" a) specified in Annex I of the Pressure Equipment Directive 2014/68/EU or b) Schedule 2 of Statutory Instruments 2016 No. 1105. Devices bearing this marking (PED or PESR) are suitable for the following types of medium: Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to |
| | 0.5 bar (7.3 psi) Devices not bearing this marking (without PED or PESR) are designed and manufactured according to sound engineering practice. They meet the requirements of a) Art. 4 Para. 3 of the Pressure Equipment Directive 2014/68/EU or |
| | b) Part 1, Para. 8 of Statutory Instruments 2016 No. 1105. The scope of application is indicated a) in diagrams 6 to 9 in Annex II of the Pressure Equipment Directive 2014/68/EU or b) Schedule 3, Para. 2 of Statutory Instruments 2016 No. 1105. |
| Additional certification | PWIS-free |
| | PWIS = paint-wetting impairment substances |

PWIS = paint-wetting impairment substances

Order code for "Service":

- Option HC: PWIS-free (version A)
- Option **HD**: PWIS-free (version B)
- Option HE: PWIS-free (version C)

For more information on PWIS-free certification, see "Test specification" document TS01028D

| guidelines Degrees of protection provided by enclosures (IP code) EN 61010-1 Safety requirements for electrical equipment for measurement, control and L general requirements EN 61326-1/-2-3 EMC requirements for electrical equipment for measurement, control and lat NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory cor NAMUR NE 32 Data retention in the event of a power failure in field and control instrument microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 131 Requirements for field devices for standard applications ETSI EN 300 328 ETSI EN 300 328 | |
|---|------------------|
| Safety requirements for electrical equipment for measurement, control and L general requirements EN 61326-1/-2-3 EMC requirements for electrical equipment for measurement, control and late NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory cortice NAMUR NE 32 Data retention in the event of a power failure in field and control instrument microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 131 Requirements for field devices for standard applications | |
| general requirements EN 61326-1/-2-3 EMC requirements for electrical equipment for measurement, control and lal NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory cor NAMUR NE 32 Data retention in the event of a power failure in field and control instrument microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field de NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | |
| EMC requirements for electrical equipment for measurement, control and late NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory cortion NAMUR NE 32 Data retention in the event of a power failure in field and control instrument microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 131 Requirements for field devices for standard applications | aboratory use - |
| NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory cor NAMUR NE 32 Data retention in the event of a power failure in field and control instrument microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | |
| NAMUR NE 32 Data retention in the event of a power failure in field and control instrument microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 | oratory use |
| microprocessors NAMUR NE 43 Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | trol equipment |
| Standardization of the signal level for the breakdown information of digital t analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | s with |
| analog output signal. NAMUR NE 53 Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | |
| Software of field devices and signal-processing devices with digital electronic NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field de NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | ransmitters with |
| NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | |
| Specifications for integrating fieldbus devices in engineering tools for field de NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | S |
| NAMUR NE 107 Self-monitoring and diagnosis of field devices NAMUR NE 131 Requirements for field devices for standard applications | |
| NAMUR NE 131 Requirements for field devices for standard applications | evices |
| NAMUR NE 131 Requirements for field devices for standard applications | |
| | |
| ETSI EN 300 328 | |
| | |
| Guidelines for 2.4 GHz radio components. | |
| ■ EN 301489 | |
| Electromagnetic compatibility and radio spectrum matters (ERM). | |

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

- 1. Select the product using the filters and search field.
- 2. Open the product page.
- 3. Select Configuration.

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

| Diagnostic functionality | Order code for "Application package", option EA "Extended HistoROM" | | | | | | |
|--------------------------|---|--|--|--|--|--|--|
| | Comprises extended functions concerning the event log and the activation of the measured value memory. | | | | | | |
| | Event log: Memory volume is extended from 20 message entries (standard version) to up to 100 entries. | | | | | | |
| | Data logging (line recorder): Memory capacity for up to 1000 measured values is activated. 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user. Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server. | | | | | | |
| | For detailed information, see the Operating Instructions for the device. | | | | | | |
| Heartbeat Technology | Order code for "Application package", option EB "Heartbeat Verification + Monitoring" | | | | | | |
| | Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". Functional testing in the installed state without interrupting the process. Traceable verification results on request, including a report. Simple testing process via local operation or other operating interfaces. Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. Extension of calibration intervals according to operator's risk assessment. | | | | | | |
| | Heartbeat Monitoring Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to: Draw conclusions - using these data and other information - about the impact process influences (e.g. buildup, interference from the magnetic field) have on the measuring performance over time. Schedule servicing in time. Monitor the process or product quality. | | | | | | |
| | For detailed information, see the Special Documentation for the device. | | | | | | |
| Cleaning | Order code for "Application package", option EC "ECC electrode cleaning " | | | | | | |
| | The electrode cleaning circuit (ECC) function has been developed to have a solution for applications where magnetite (Fe ₃ O ₄) deposits frequently occur (e.g. hot water). Since magnetite is highly conductive this build up leads to measuring errors and ultimately to the loss of signal. The application package is designed to avoid build-up of very conductive matter and thin layers (typical of magnetite). | | | | | | |
| | For detailed information, see the Operating Instructions for the device. | | | | | | |
| OPC-UA Server | Order code for "Application package", option EL "OPC-UA Server" | | | | | | |
| | The application package provides an integrated OPC-UA server for comprehensive device services for IoT and SCADA applications. | | | | | | |
| | For detailed information, see the Special Documentation for the device. | | | | | | |

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the transmitter

| Accessories | Description |
|--|---|
| Proline 300 transmitter | Transmitter for replacement or storage. Use the order code to define the following specifications: Approvals Output Input Display/operation Housing Software Order code: 5X3BXX Installation Instructions EA01199D |
| Remote display and operating module DKX001 | If ordered directly with the measuring device: Order code for "Display; operation", option O "Remote display 4-line, illuminated; 10 m (30 ft) cable; touch control" If ordered separately: Measuring device: order code for "Display; operation", option M "W/o, prepared for remote display" DKX001: Via the separate product structure DKX001 If ordered subsequently: DKX001: Via the separate product structure DKX001 |
| | Mounting bracket for DKX001 If ordered directly: order code for "Accessory enclosed", option RA "Mounting bracket, pipe 1/2" If ordered subsequently: order number: 71340960 |
| | Connecting cable (replacement cable) Via the separate product structure: DKX002 |
| | Further information on display and operating module DKX001 $\rightarrow \square$ 104. |
| | Special Documentation SD01763D |
| External WLAN antenna | External WLAN antenna with 1.5 m (59.1 in) connecting cable and two angle brackets. Order code for "Accessory enclosed", option P8 "Wireless antenna wide area". |
| | The external WLAN antenna is not suitable for use in hygienic applications. Additional information regarding the WLAN interface → |
| | Order number: 71351317 |
| | Installation Instructions EA01238D |
| Weather protection cover | Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight. |
| | Order number: 71343505 |
| | Installation Instructions EA01160D |

For the sensor

| Accessories | Description |
|-------------|--|
| Adapter set | Adapter connections for installing a Promag H instead of a Promag 30/33 A or Promag 30/33 H (DN 25). |
| | Consists of: • 2 process connections • Screws • Seals |
| Seal set | For the regular replacement of seals for the sensor. |

| Spacer | If replacing a DN $80/100\ sensor$ in an existing installation, a spacer is needed if the new sensor is shorter. |
|-------------------|--|
| Welding jig | Welding socket as process connection: welding jig for installation in pipe. |
| Grounding rings | Are used to ground the medium in lined measuring tubes to ensure proper measurement. |
| | Grounding rings can be ordered via the device order structure or configured and ordered as an accessory via the DK5HR order structure. |
| Mounting kit | Consists of: • 2 process connections • Screws • Seals |
| Wall mounting kit | Wall mounting kit for measuring device (only DN 2 to 25 (1/12 to 1")) |

| Communication-specific accessories | Accessories | Description |
|---------------------------------------|------------------------------|--|
| accessories | Commubox FXA195 | For intrinsically safe HART communication with FieldCare via the USB port |
| | HART | Technical Information TI00404F |
| | HART Loop Converter HMX50 | Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. |
| | | Technical Information TI00429F Operating Instructions BA00371F |
| | Fieldgate FXA42 | Transmission of the measured values of connected 4 to 20 mA analog measuring devices, as well as digital measuring devices |
| | | Technical Information TI01297S Operating Instructions BA01778S Product page: www.endress.com/fxa42 |
| | Field Xpert SMT50 | The Field Xpert SMT50 table PC for device configuration enables mobile plant asset management. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle. |
| | | Technical Information TI01555S Operating Instructions BA02053S Product page: www.endress.com/smt50 |
| | Field Xpert SMT70 | The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle. |
| | | Technical Information TI01342S Operating Instructions BA01709S Product page: www.endress.com/smt70 |
| | Field Xpert SMT77 | The Field Xpert SMT77 tablet PC for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1. |
| | | Technical Information TI01418S Operating Instructions BA01923S Product page: www.endress.com/smt77 |

| Service-specific accessories | Accessories | Description |
|------------------------------|-------------|--|
| | Applicator | Software for selecting and sizing Endress+Hauser measuring devices: Choice of measuring devices for industrial requirements Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy. Graphic illustration of the calculation results Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project. Applicator is available: Via the Internet: https://portal.endress.com/webapp/applicator As a downloadable DVD for local PC installation. |
| | Netilion | lloT ecosystem: Unlock knowledge Endress+Hauser 's Netilion lloT ecosystem enables you to optimize your plant performance, digitize workflows, share knowledge and improve collaboration. Based on decades of experience in process automation, Endress+Hauser offers the process industry an lloT ecosystem that enables you to gain useful insights from data. This knowledge can be used to optimize processes, leading to higher plant availability, efficiency and reliability, and ultimately to a more profitable plant. www.netilion.endress.com |
| | FieldCare | FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition. |
| | DeviceCare | Tool to connect and configure Endress+Hauser field devices. |
| | DeviceCare | Innovation brochure IN01047S |

| System components | Accessories | Description |
|-------------------|-------------------------------------|---|
| | Memograph M graphic data manager | The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick. |
| | | Technical Information TI00133R Operating Instructions BA00247R |
| | ITEMP | The temperature transmitters can be used in all applications and are suitable for the measurement of gases, steam and liquids. They can be used to read in the medium temperature. |
| | | "Fields of Activity" document FA00006T |

Supplementary documentation

For an overview of the scope of the associated Technical Documentation, refer to the following:
 Device Viewer (www.endress.com/deviceviewer): Enter the serial number from the nameplate

• *Endress+Hauser Operations app*: Enter serial number from nameplate or scan matrix code on nameplate.

Standard documentation

i

Supplementary information on the semi-standard options is available in the relevant Special Documentation in the TSP database.

Brief Operating Instructions

Brief Operating Instructions for the sensor

| Measuring device | Documentation code |
|------------------|--------------------|
| Proline Promag H | KA01289D |

Brief Operating Instructions for the transmitter

| | Documentation code | | | | | | | |
|------------------|--------------------|-------------------------|----------------|----------------|-----------------|-------------|----------|--------------------------------------|
| Measuring device | HART | FOUNDATIO N Fieldbus | PROFIBUS PA | PROFIBUS DP | Modbus RS485 | EtherNet/IP | PROFINET | PROFINET with Ethernet- APL |
| Proline 300 | KA01308D | KA01294D | KA01405D | KA01385D | KA01310D | KA01338D | KA01340D | KA01516D |

Operating Instructions

| Measuring device | Documentatio | Documentation code | | | | | | |
|------------------|--------------|-------------------------|----------------|----------------|--------------|-------------|----------|--------------------------------------|
| | HART | FOUNDATIO N Fieldbus | PROFIBUS PA | PROFIBUS DP | Modbus RS485 | EtherNet/IP | PROFINET | PROFINET with Ethernet- APL |
| Promag H 300 | BA01392D | BA01477D | BA01396D | BA01865D | BA01394D | BA01716D | BA01718D | BA02106D |

Description of Device Parameters

| Measuring device | Documentatio | Documentation code | | | | | | |
|------------------|--------------|-------------------------|----------------|----------------|-----------------|-------------|----------|--------------------------------------|
| | HART | FOUNDATIO N Fieldbus | PROFIBUS PA | PROFIBUS DP | Modbus RS485 | EtherNet/IP | PROFINET | PROFINET with Ethernet- APL |
| Promag 300 | GP01051D | GP01098D | GP01052D | GP01135D | GP01053D | GP01113D | GP01112D | GP01172D |

Supplementary devicedependent documentation

Safety instructions

Safety instructions for electrical equipment for hazardous areas.

| Contents | Documentation code |
|-----------------------|--------------------|
| ATEX/IECEx Ex d/Ex de | XA01414D |
| ATEX/IECEx Ex ec | XA01514D |
| cCSAus XP | XA01515D |
| cCSAus Ex d/ Ex de | XA01516D |
| cCSAus Ex nA | XA01517D |
| INMETRO Ex d/Ex de | XA01518D |
| INMETRO Ex ec | XA01519D |
| NEPSI Ex d/Ex de | XA01520D |
| NEPSI Ex nA | XA01521D |
| EAC Ex d/Ex de | XA01656D |
| EAC Ex nA | XA01657D |
| JPN Ex d | XA01775D |

Remote display and operating module DKX001

| Contents | Documentation code |
|------------------|--------------------|
| ATEX/IECEx Ex i | XA01494D |
| ATEX/IECEx Ex ec | XA01498D |
| cCSAus IS | XA01499D |
| cCSAus Ex nA | XA01513D |
| INMETRO Ex i | XA01500D |
| INMETRO Ex ec | XA01501D |
| NEPSI Ex i | XA01502D |
| NEPSI Ex nA | XA01503D |

Functional Safety Manual

| Contents | Documentation code |
|------------|--------------------|
| Promag 300 | SD01740D |

Special Documentation

| Contents | Documentation code |
|---|--------------------|
| Information on the Pressure Equipment Directive | SD01614D |
| Radio approvals for WLAN interface for A309/A310 display module | SD01793D |
| Remote display and operating module DKX001 | SD01763D |
| OPC-UA server ¹⁾ | SD02043D |

1) This Special Documentation is only available for device versions with a HART output.

| Contents | Documentation code | | | | | | | |
|----------------------|--------------------|-------------------------|----------------|----------------|-----------------|----------|-------------|--------------------------------------|
| | HART | FOUNDATIO N Fieldbus | PROFIBUS PA | PROFIBUS DP | Modbus RS485 | PROFINET | EtherNet/IP | PROFINET with Ethernet- APL |
| Heartbeat Technology | SD01640D | SD01742D | SD01744D | SD02206D | SD01743D | SD01986D | SD01980D | SD02729D |
| Web server | SD01654D | SD01657D | SD01656D | SD02235D | SD01655D | SD01977D | SD01976D | SD02768D |

Installation instructions

| Contents | Note | | |
|---|--|--|--|
| Installation instructions for spare part sets and accessories | Documentation code: specified for each individual accessory $\rightarrow \triangleq 121$. | | |

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas USA

PROFIBUS®

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

FOUNDATION™ Fieldbus

Registration-pending trademark of the FieldComm Group, Austin, Texas, USA

Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

EtherNet/IP™

Trademark of ODVA, Inc.

Ethernet-APL™

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

PROFINET®

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA



www.addresses.endress.com

