Technical Information **Proline Promass F 300**

Coriolis flowmeter



Flowmeter with premium accuracy, robustness and a compact, easily accessible transmitter

Application

- Measuring principle operates independently of physical fluid properties such as viscosity or density
- Highest measurement performance for liquids and gases under varying, demanding process conditions

Device properties

- \blacksquare Mass/volume flow: measurement error ±0.05 %
- Medium temperature: -196 to +350 °C (-320 to +662 °F)
- Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10")
- Compact dual-compartment housing with up to 3 I/Os
- Backlit display with touch control and WLAN access
- Remote display available

Your benefits

- Highest process safety immune to fluctuating and harsh environments
- Fewer process measuring points multivariable measurement (flow, density, temperature)
- Space-saving installation no in-/outlet run needs
- Full access to process and diagnostic information numerous, freely combinable I/Os and Ethernet
- Reduced complexity and variety freely configurable I/O functionality
- Integrated verification Heartbeat Technology



Table of contents

About this document		Environment	
Symbols	. 4	Ambient temperature range	
		Storage temperature	60
Function and system design	5	Climate class	60
Measuring principle		Relative humidity	60
Measuring system	. 7	Operating height	
Equipment architecture		Degree of protection	60
Reliability		Shock and vibration resistance	
•		Internal cleaning	
T	11	Mechanical load	60
Input	11	Electromagnetic compatibility (EMC)	6.
Measuring range		Process	6
Operable flow range		Medium temperature range	
Input signal	12	Pressure-temperature ratings	
		Sensor housing	
Output	14	Rupture disk	
Output and input variants		Flow limit	
Output and input variants	16	Pressure loss	
Signal on alarm	I		
3		Static pressure	
Ex connection data	I	Thermal insulation	
	25	Heating	
Low flow cut off	26	Vibrations	6
Galvanic isolation	27		
Protocol-specific data	27	Custody transfer	70
Power supply	33		_
Terminal assignment	I	Mechanical construction	
Available device plugs	34	Dimensions in SI units	
Supply voltage	35	Dimensions in US units	
Power consumption	I	Weight	
Current consumption	35	Materials	104
Power supply failure	35	Process connections	10
Overcurrent protection element	35	Surface roughness	10
Electrical connection	36	-	
Potential equalization	47	Display and user interface	100
Terminals	47	Operation concept	
Cable entries	47	3 3	108
Pin assignment, device plug			108
Cable specification		Remote operation	
Overvoltage protection	50	Service interface	
		Network integration	
Performance characteristics	51	Supported operating tools	
Reference operating conditions	51	HistoROM data management	118
Maximum measurement error	51		
Repeatability	53	Certificates and approvals	120
Response time	53	CE mark	
Influence of ambient temperature	54		120
Influence of medium temperature	54		120
Influence of medium pressure	54	<u> </u>	120
			122
Design fundamentals	ر ر	HART certification	
Mounting	56		122
Installation point	56		122
Orientation	57	EtherNet/IP certification	
Inlet and outlet runs	58	Certification PROFINET	
Special mounting instructions	58	PROFINET with Ethernet-APL certification	
opecial insulining instructions		Pressure Equipment Directive	123

2

Radio approval	123
Measuring instrument approval	123
Additional certification	123
External standards and guidelines	124
Zinterma ottanuar ao ama garatimito	12
Ordering information	125
Application packages	125
Diagnostic functionality	125
Heartbeat Technology	125
Concentration measurement	126
Special density	126
Extended density	126
Petroleum	126
Petroleum & locking function	127
OPC-UA Server	127
Accessories	127
Device-specific accessories	127
Communication-specific accessories	128
Service-specific accessories	129
System components	130
Supplemental documentation	130
Standard documentation	
Supplementary device-dependent documentation	13
Registered trademarks	127
neuisteieu tiaueiliaiks	12

About this document

Symbols Electrical symbols

Symbol	Meaning
===	Direct current
~	Alternating current
$\overline{\sim}$	Direct current and alternating current
=	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Potential equalization connection (PE: protective earth) Ground terminals that must be connected to ground prior to establishing any other connections.
	The ground terminals are located on the interior and exterior of the device: Interior ground terminal: potential equalization is connected to the supply network. Exterior ground terminal: device is connected to the plant grounding system.

Communication-specific symbols

Symbol	Meaning
?	Wireless Local Area Network (WLAN) Communication via a wireless, local network.

Symbols for certain types of information

Symbol	Meaning
✓	Permitted Procedures, processes or actions that are permitted.
✓ ✓	Preferred Procedures, processes or actions that are preferred.
X	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
Ţ <u>i</u>	Reference to documentation
A=	Reference to page
	Reference to graphic
	Visual inspection

Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections

Symbol	Meaning
EX	Hazardous area
×	Safe area (non-hazardous area)
≋➡	Flow direction

Function and system design

Measuring principle

The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present in a system when both translational and rotational movements are superimposed.

 $F_c = 2 \cdot \Delta m (v \cdot \omega)$

 F_c = Coriolis force

 $\Delta m = moving mass$


 ω = rotational velocity

v = radial velocity in rotating or oscillating system

The amplitude of the Coriolis force depends on the moving mass Δm , its velocity v in the system and thus on the mass flow. Instead of a constant rotational velocity ω , the sensor uses oscillation.

In the sensor, two parallel measuring tubes containing flowing fluid oscillate in antiphase, acting like a tuning fork. The Coriolis forces produced at the measuring tubes cause a phase shift in the tube oscillations (see illustration):

- At zero flow (when the fluid is at a standstill) the two tubes oscillate in phase (1).
- Mass flow causes deceleration of the oscillation at the inlet of the tubes (2) and acceleration at the outlet (3).



A0028850

The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube oscillations at the inlet and outlet. System balance is ensured by the antiphase oscillation of the two measuring tubes. The measuring principle operates independently of temperature, pressure, viscosity, conductivity and flow profile.

Density measurement

The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising measuring tube and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. The resonance frequency is thus a function of the medium density. The microprocessor utilizes this relationship to obtain a density signal.

Volume measurement


Together with the measured mass flow, this is used to calculate the volume flow.

Temperature measurement

The temperature of the measuring tube is determined in order to calculate the compensation factor due to temperature effects. This signal corresponds to the process temperature and is also available as an output signal.

Gas Fraction Handler (GFH)

The Gas Fraction Handler is a Promass software function that improves measurement stability and repeatability. The function continuously checks for the presence of disturbances in single-phase flow, i.e. gas bubbles in liquids or droplets in gas. In the presence of the second phase, flow and density become increasingly unstable. The Gas Fraction Handler function improves measurement stability with respect to the severity of the disturbances, without any effect under single-phase flow conditions.



Measuring system

The device consists of a transmitter and a sensor.


The device is available as a compact version:

The transmitter and sensor form a mechanical unit.

A0026708

Transmitter

Proline 300



Device versions and materials:


- Transmitter housing
- Aluminum, coated: aluminum, AlSi10Mg, coated
- Stainless, hygienic: stainless steel, 1.4404
- Cast, stainless: cast, stainless steel, 1.4409 (CF3M) similar to 316L
- Material of window in transmitter housing:
 - Aluminum, coated: glass
 - Stainless, hygienic: polycarbonate
 - Cast, stainless: glass

Configuration:

- External operation via 4-line, illuminated graphic local display (LCD) with touch control and guided menus ("Make-it-run" wizards) for application-specific commissioning.
- Via service interface or WLAN interface:
 - Operating tools (e.g. FieldCare, DeviceCare)
 - Web server (access via Web browser, e.g. Microsoft Internet Explorer, Microsoft Edge)


Sensor

Promass F



- Bent dual-tube system
- Excellent performance across a wide range of applications
- Simultaneous measurement of flow, volume flow, density and temperature (multivariable)
- Immune to process influences
- Nominal diameter range: DN 8 to 250 ($\frac{3}{8}$ to 10")
- Materials:
 - Sensor: stainless steel, 1.4301 (304); optional 1.4404 (316/316L)
 - Measuring tubes: stainless steel, 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)
 - Process connections: stainless steel, 1.4404 (316/316L); 1.4301 (304); Alloy C22, 2.4602 (UNS N06022)

Equipment architecture



 \blacksquare 1 Possibilities for integrating measuring devices into a system

- 1 Control system (e.g. PLC)
- 2 Connecting cable (0/4 to 20 mA HART etc.)
- 3 Fieldbus
- 4 Coupler
- 5 Non-hazardous area
- 6 Hazardous area: Zone 2; Class I, Division 2
- 7 Hazardous area: Zone 1; Class I, Division 1

Reliability

IT security

Our warranty is valid only if the product is installed and used as described in the Operating Instructions. The product is equipped with security mechanisms to protect it against any inadvertent changes to the settings.

IT security measures, which provide additional protection for the product and associated data transfer, must be implemented by the operators themselves in line with their security standards.

Device-specific IT security

The device offers a range of specific functions to support protective measures on the operator's side. These functions can be configured by the user and guarantee greater in-operation safety if used correctly. The following list provides an overview of the most important functions:

Function/interface	Factory setting	Recommendation
Write protection via hardware write protection switch $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $	Not enabled	On an individual basis following risk assessment
Access code (also applies to web server login or FieldCare connection) → 🖺 9	Not enabled (0000)	Assign a customized access code during commissioning
WLAN (order option in display module)	Enabled	On an individual basis following risk assessment
WLAN security mode	Enabled (WPA2- PSK)	Do not change
WLAN passphrase (Password) → 🖺 9	Serial number	Assign an individual WLAN passphrase during commissioning
WLAN mode	Access point	On an individual basis following risk assessment
Web server → 🖺 9	Enabled	On an individual basis following risk assessment
Service interface CDI-RJ45 → 🖺 10	_	On an individual basis following risk assessment

Protecting access via hardware write protection

Write access to the parameters of the device via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare) can be disabled via a write protection switch (DIP switch on the main electronics module). When hardware write protection is enabled, only read access to the parameters is possible.

Hardware write protection is disabled when the device is delivered.

Protecting access via a password

Different passwords are available to protect write access to the device parameters or access to the device via the WLAN interface.

- User-specific access code
 - Protect write access to the device parameters via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare). Access authorization is clearly regulated through the use of a user-specific access code.
- WLAN passphrase
- The network key protects a connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface which can be ordered as an option.
- Infrastructure mode
 - When the device is operated in infrastructure mode, the WLAN passphrase corresponds to the WLAN passphrase configured on the operator side.

User-specific access code

Write access to the device parameters via the local display, web browser or operating tool (e.g. FieldCare, DeviceCare) can be protected by the modifiable, user-specific access code.

WLAN passphrase: Operation as WLAN access point

A connection between an operating unit (e.g. notebook or tablet) and the device via the WLAN interface, which can be ordered as an optional extra, is protected by the network key. The WLAN authentication of the network key complies with the IEEE 802.11 standard.

When the device is delivered, the network key is pre-defined depending on the device. It can be changed via the **WLAN settings** submenu in the **WLAN passphrase** parameter.

Infrastructure mode

A connection between the device and WLAN access point is protected by means of an SSID and passphrase on the system side. Please contact the relevant system administrator for access.

General notes on the use of passwords

- The access code and network key supplied with the device should be changed during commissioning for safety reasons.
- Follow the general rules for generating a secure password when defining and managing the access code and network key.
- The user is responsible for the management and careful handling of the access code and network key.

Access via web server

The device can be operated and configured via a web browser with the integrated web server. The connection is established via the service interface (CDI-RJ45) or the WLAN interface. For device versions with the EtherNet/IP and PROFINET communication protocols, the connection can also be established via the terminal connection for signal transmission with EtherNet/IP, PROFINET (RJ45 plug) or PROFINET with Ethernet-APL (two-wire).

The web server is enabled when the device is delivered. The web server can be disabled via the **Web server functionality** parameter if necessary (e.g., after commissioning).

The device and status information can be hidden on the login page. This prevents unauthorized access to the information.

Detailed information on the device parameters:

"Description of device parameters" document $\rightarrow \implies 131$.

Access via OPC-UA

The device can communicate with OPC UA clients using the "OPC UA Server" application package.

The OPC UA server integrated in the device can be accessed via the WLAN access point using the WLAN interface - which can be ordered as an optional extra - or the service interface (CDI- RJ45) via Ethernet network. Access rights and authorization as per separate configuration.

The following Security Modes are supported as per the OPC UA Specification (IEC 62541):

- None
- Basic128Rsa15 signed
- Basic128Rsa15 signed and encrypted

Access via service interface (CDI-RJ45)

The device can be connected to a network via the service interface (CDI-RJ45). Device-specific functions guarantee the secure operation of the device in a network.

The use of relevant industrial standards and guidelines that have been defined by national and international safety committees, such as IEC/ISA62443 or the IEEE, is recommended. This includes organizational security measures such as the assignment of access authorization as well as technical measures such as network segmentation.

- Transmitters with an Ex de approval may not be connected via the service interface (CDI-RJ45)!

 Order code for "Approval transmitter + sensor", options (Ex de): BA, BB, C1, C2, GA, GB, MA, MB, NA, NB BB, C2, GB, MB, NB

Input

Measured variable

Direct measured variables

- Mass flow
- Density
- Temperature

Calculated measured variables

- Volume flow
- Corrected volume flow
- Reference density

Measuring range

Measuring range for liquids


DN		Measuring range full scale values $\dot{m}_{min(F)}$ to $\dot{m}_{max(F)}$	
[mm]	[in]	[kg/h]	[lb/min]
8	3/8	0 to 2 000	0 to 73.50
15	1/2	0 to 6 500	0 to 238.9
25	1	0 to 18 000	0 to 661.5
40	1½	0 to 45 000	0 to 1654
50	2	0 to 70 000	0 to 2 573
80	3	0 to 180 000	0 to 6615
100	4	0 to 350 000	0 to 12860
150	6	0 to 800 000	0 to 29400
250	10	0 to 2 200 000	0 to 80 850

Measuring range for gases

The full scale value depends on the density and the sound velocity of the gas used. The full scale value can be calculated with the following formulas:

$$\dot{m}_{\text{max}(G)} = (\rho_G \cdot (c_G/m) \cdot d_i^2 \cdot (\pi/4) \cdot 3600 \cdot n)$$

m _{max(G)}	Maximum full scale value for gas [kg/h]
ρ_{G}	Gas density in [kg/m³] at operating conditions
c_{G}	Sound velocity (gas) [m/s]
d _i	Measuring tube internal diameter [m]
π	Pi
n = 2	Number of measuring tubes
m = 2	For all gases except pure H2 and He gas
m = 3	For pure H2 and He gas



Recommended measuring range

Flow limit → 🖺 68

Operable flow range

Over 1000:1.

Flow rates above the preset full scale value do not override the electronics unit, with the result that the totalizer values are registered correctly.

Input signal

Output and input variants

→ 🖺 14

External measured values

To increase the measurement accuracy of certain measured variables or to calculate the corrected volume flow for gases, the automation system can continuously write different measured values to the measuring instrument:

- Operating pressure to increase measurement accuracy (Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S)
- Medium temperature to increase measurement accuracy (e.g. iTEMP)
- Reference density for calculating the corrected volume flow for gases
- Various pressure and temperature measuring devices can be ordered from Endress+Hauser: see "Accessories" section → 🖺 130

It is recommended to read in external measured values to calculate the corrected volume flow.

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Current input

Digital communication

The measured values can be written by the automation system via:

- FOUNDATION Fieldbus
- PROFIBUS DP
- PROFIBUS PA
- Modbus RS485
- Modbus TCP over Ethernet-APL
- Ethernet/IP
- PROFINET
- PROFINET over Ethernet-APL

Current input 0/4 to 20 mA

Current input	0/4 to 20 mA (active/passive)
Current span	 4 to 20 mA (active) 0/4 to 20 mA (passive)
Resolution	1 μΑ
Voltage drop	Typically: 0.6 to 2 V for 3.6 to 22 mA (passive)
Maximum input voltage	≤ 30 V (passive)
Open-circuit voltage	≤ 28.8 V (active)
Possible input variables	PressureTemperatureDensity

Status input

Maximum input values	■ DC −3 to 30 V ■ If status input is active (ON): R _i >3 kΩ
Response time	Configurable: 5 to 200 ms

Input signal level	 Low signal: DC -3 to +5 V High signal: DC 12 to 30 V
Assignable functions	 Off Reset the individual totalizers separately Reset all totalizers Flow override

Output

Output and input variants

Depending on the option selected for output/input 1, different options are available for the other outputs and inputs. Only one option can be selected for each output/input 1 to 3. The following tables must be read vertically (\downarrow) .

Example: If the option BA "4-20 mA HART" was selected for output/input 1, one of the options A, B, D, E, F, H, I or J is available for output 2 and one of the options A, B, D, E, F, H, I or J is available for output 3.

Output/input 1 and options for output/input 2



Order code for "Output; input 1" (020) →			Possible options											
Current output 4 to 20 mA HART	BA													
Current output 4 to 20 mA HART Ex i passive	1	CA												
Current output 4 to 20 mA HART Ex i active		4	СС											
FOUNDATION Fieldbus			\	SA										
FOUNDATION Fieldbus Ex i				4	TA									
PROFIBUS DP					4	LA								
PROFIBUS PA						\	GA							
PROFIBUS PA Ex i							4	НА						
Modbus RS485								\	MA					
EtherNet/IP 2-port switch integrated									\	NA				
PROFINET 2-port switch integrated										→	RA			
PROFINET over Ethernet-APL											\	RB		
PROFINET over Ethernet-APL Ex i												1	RC	
Order code for "Output; input 2" (021) →	+	4	\	\	\	\	\	\	\	→	4	4	\	
Not used	А	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	
Current output 4 to 20 mA	В			В		В	В		В	В	В	В		
Current output 4 to 20 mA Ex i passive		С	С		С			С					С	
User-configurable input/output 1)	D			D		D	D		D	D	D	D		
Pulse/frequency/switch output	Е			Е		Е	Е		Е	E	Е	Е		
Double pulse output ²⁾	F								F					
Pulse/frequency/switch output Ex i passive		G	G		G			G					G	
Relay output	Н			Н		Н	Н		Н	Н	Н	Н		
Current input 0/4 to 20 mA	I			I		I	I		I	I	I	I		
Status input	T			J		J	J		J	J	J	J		

²⁾ If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for selection for output/input 3 (022).

Output/input 1 and options for output/input 3

Order code for "Output; input 1" (020) →				Possi	ble o	ption	.s						
Current output 4 to 20 mA HART	ВА												
Current output 4 to 20 mA HART Ex i passive	\	CA											
Current output 4 to 20 mA HART Ex i active		1	СС										
FOUNDATION Fieldbus			4	SA									
FOUNDATION Fieldbus Ex i				\	TA								
PROFIBUS DP					\	LA							
PROFIBUS PA						4	GA						
PROFIBUS PA Ex i							4	НА					
Modbus RS485								4	MA				
EtherNet/IP 2-port switch integrated									\	NA			
PROFINET 2-port switch integrated										1	RA		
PROFINET over Ethernet-APL/SPE, 10 Mbit/s, 2-wire											\	RB	
PROFINET over Ethernet-APL Ex i, 10 Mbit/s, 2-wire												4	RC
Order code for "Output; input 3" (022) →		4	4	\	\	4	\	\	\	4	\	\	\
Not used	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α	Α
Current output 4 to 20 mA	В					В			В	В	В	В	
Current output 4 to 20 mA Ex i passive		С	С										
User-configurable input/output	D					D			D	D	D	D	
Pulse/frequency/switch output	Е					Е			Е	Е	E	E	
Double pulse output (slave) 1)	F								F				
Pulse/frequency/switch output Ex i passive		G	G										
Relay output	Н					Н			Н	Н	Н	Н	
Current input 0/4 to 20 mA	I					I			I	I	I	I	
Status input	J					J			J	J	J	J	

¹⁾ If double pulse output (F) is selected for output/input 2 (021), only the double pulse output (F) option is available for output/input 3 (022).

Output signal

Current output 4 to 20 mA HART

Order code	"Output; input 1" (20): Option BA: current output 4 to 20 mA HART
Signal mode	Can be set to: Active Passive
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA (only if the signal mode is active) Fixed current
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	250 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature Electronics temperature Oscillation frequency 0 Oscillation damping 0 Signal asymmetry Exciter current 0 The range of options increases if the measuring device has one or more application packages.

Current output 4 to 20 mA HART Ex i

Order code	"Output; input 1" (20) choose from: Option CA: current output 4 to 20 mA HART Ex i passive Option CC: current output 4 to 20 mA HART Ex i active
Signal mode	Depends on the selected order version.
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA for independent of the signal mode is active) Fixed current
Open-circuit voltage	DC 21.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	 250 to 400 Ω (active) 250 to 700 Ω (passive)
Resolution	0.38 μΑ

Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature Electronics temperature Oscillation frequency 0 Oscillation damping 0 Signal asymmetry Exciter current 0 The range of options increases if the measuring device has one or more application packages.

FOUNDATION Fieldbus

FOUNDATION Fieldbus	H1, IEC 61158-2, galvanically isolated
Data transfer	31.25 kbit/s
Current consumption	10 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud
Terminating resistor	Integrated, can be activated via DIP switches

PROFIBUS PA

PROFIBUS PA	In accordance with EN 50170 Volume 2, IEC 61158-2 (MBP), galvanically isolated
Data transmission	31.25 kbit/s
Current consumption	10 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

Modbus RS485

Physical interface	RS485 in accordance with EIA/TIA-485 standard
Terminating resistor	Integrated, can be activated via DIP switches

EtherNet/IP

Standards In accordance with IEEE 802.3

PROFINET

Standards	In accordance with IEEE 802.3

PROFINET with Ethernet-APL

Device use	Device connection to an APL field switch The device may only be operated according to the following APL port classifications: ■ If used in hazardous areas: SLAA or SLAC ¹¹ ■ If used in non-hazardous areas: SLAX Connection values of APL field switch (corresponds to APL port classification SPCC or SPAA, for instance):
	 Maximum input voltage: 15 V_{DC} Minimum output values: 0.54 W
	 Device connection to an SPE switch In non-hazardous areas, the device can be used with an appropriate SPE switch: The device can be connected to an SPE switch with a maximum voltage of 30 V_{DC} and a minimum output power of 1.85 W connected. The SPE switch must support the 10BASE-T1L standard and PoDL power classes 10, 11 or 12 and have a function to disable power class detection.
PROFINET	According to IEC 61158 and IEC 61784
Ethernet-APL	According to IEEE 802.3cg, APL port profile specification v1.0, galvanically isolated
Data transmission	10 Mbit/s
Current consumption	Transmitter ■ Max. 400 mA(24 V) ■ Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)
Permitted supply voltage	9 to 30 V
Network connection	With integrated reverse polarity protection

1) For more information on using the device in the hazardous area, see the Ex-specific Safety Instructions

Current output 4 to 20 mA

Order code	"Output; input 2" (21), "Output; input 3" (022): Option B: current output 4 to 20 mA
Signal mode	Can be set to: Active Passive
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA 0 to 20 mA for independent of the signal mode is active) Fixed current
Maximum output values	22.5 mA
Open-circuit voltage	DC 28.8 V (active)
Maximum input voltage	DC 30 V (passive)
Load	0 to 700Ω
Resolution	0.38 μΑ

Damping	Configurable: 0 to 999.9 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature Electronics temperature Oscillation frequency 0 Oscillation damping 0 Signal asymmetry Exciter current 0 The range of options increases if the measuring device has one or more application packages.

Current output 4 to 20 mA Ex i passive

Order code	"Output; input 2" (21), "Output; input 3" (022): Option C: current output 4 to 20 mA Ex i passive
Signal mode	Passive
Current range	Can be set to: 4 to 20 mA NAMUR 4 to 20 mA US 4 to 20 mA Fixed current
Maximum output values	22.5 mA
Maximum input voltage	DC 30 V
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Configurable: 0 to 999 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature Electronics temperature Oscillation frequency 0 Oscillation damping 0 Signal asymmetry Exciter current 0 The range of options increases if the measuring device has one or more application packages.

Pulse/frequency/switch output

Function	Can be configured as pulse, frequency or switch output
Version	Open collector Can be set to: Active Passive Passive NAMUR
	Ex-i, passive
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Voltage drop	For 22.5 mA: ≤ DC 2 V

Pulse output	
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Pulse width	Configurable: 0.05 to 2 000 ms
Maximum pulse rate	10 000 Impulse/s
Pulse value	Configurable
Assignable measured variables	 Mass flow Volume flow Corrected volume flow The range of options increases if the measuring device has one or more application packages.
Frequency output	., .
Maximum input values	DC 30 V, 250 mA (passive)
Maximum output current	22.5 mA (active)
Open-circuit voltage	DC 28.8 V (active)
Output frequency	Configurable: end value frequency 2 to $10000Hz(f_{max}=12500Hz)$
Damping	Configurable: 0 to 999.9 s
Pulse/pause ratio	1:1
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature Electronics temperature Oscillation frequency 0 Oscillation damping 0 Signal asymmetry Exciter current 0 The range of options increases if the measuring device has one or more application packages.
Switch output	
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Switching behavior	Binary, conductive or non-conductive
Switching delay	Configurable: 0 to 100 s

Number of switching cycles	Unlimited
Assignable functions	 Disable On Diagnostic behavior Limit Mass flow Volume flow Corrected volume flow Density Reference density Temperature Totalizer 1-3 Flow direction monitoring Status Partially filled pipe detection Low flow cut off The range of options increases if the measuring device has one or more application packages.

Double pulse output

Function	Double pulse
Version	Open collector
	Can be set to: Active Passive Passive NAMUR
Maximum input values	DC 30 V, 250 mA (passive)
Open-circuit voltage	DC 28.8 V (active)
Voltage drop	For 22.5 mA: ≤ DC 2 V
Output frequency	Configurable: 0 to 1000 Hz
Damping	Configurable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature The range of options increases if the measuring device has one or more application packages.

Relay output

Function	Switch output
Version	Relay output, galvanically isolated
Switching behavior	Can be set to: NO (normally open), factory setting NC (normally closed)

Maximum switching capacity (passive)	■ DC 30 V, 0.1 A ■ AC 30 V, 0.5 A
Assignable functions	 Disable On Diagnostic behavior Limit Mass flow Volume flow Corrected volume flow Density Reference density Temperature Totalizer 1-3 Flow direction monitoring Status Partially filled pipe detection Low flow cut off
	The range of options increases if the measuring device has one or more application packages.

User-configurable input/output

One specific input or output is assigned to a user-configurable input/output (configurable I/O) during device commissioning.

The following inputs and outputs are available for assignment:

- Choice of current output: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Pulse/frequency/switch output
- Choice of current input: 4 to 20 mA (active), 0/4 to 20 mA (passive)
- Status input

The technical values correspond to those of the inputs and outputs described in this section.

Signal on alarm

Depending on the interface, failure information is displayed as follows:

HART current output

Device diagnostics	Device condition can be read out via HART Command 48
--------------------	--

PROFIBUS PA

Status and alarm messages	Diagnostics in accordance with PROFIBUS PA Profile 3.02
Failure current FDE (Fault Disconnection Electronic)	0 mA

PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

EtherNet/IP

Device diagnostics	Device condition can be read out in Input Assembly
--------------------	--

PROFINET

PROFINET with Ethernet-APL

Device diagnostics	Diagnostics according to PROFINET PA Profile 4
--------------------	--

FOUNDATION Fieldbus

Status and alarm messages	Diagnostics in accordance with FF-891
Failure current FDE (Fault Disconnection Electronic)	0 mA

Modbus RS485

Failure mode	Choose from:
	■ NaN value instead of current value
	■ Last valid value

Modbus TCP-APL

Failure mode	Choose from:
	NaN value instead of current value
	■ Last valid value

Current output 0/4 to 20 mA

4 to 20 mA

Failure mode	Choose from: 4 to 20 mA in accordance with NAMUR recommendation NE 43 4 to 20 mA in accordance with US Min. value: 3.59 mA Max. value: 22.5 mA Definable value between: 3.59 to 22.5 mA Accual value
	 Last valid value

0 to 20 mA

Failure mode	Choose from:
	 Maximum alarm: 22 mA Definable value between: 0 to 20.5 mA

Pulse/frequency/switch output

Pulse output	
Fault mode	Choose from: Actual value No pulses
Frequency output	
Fault mode	Choose from: Actual value O Hz Definable value between: 2 to 12 500 Hz

Switch output	
Fault mode	Choose from: Current status Open Closed

Relay output

Failure mode	Choose from:
	 Current status
	■ Open
	■ Closed

Local display

Plain text display	With information on cause and remedial measures
Backlight	Red lighting indicates a device error.



Status signal as per NAMUR recommendation NE 107

Interface/protocol

- Via digital communication:
 - HART protocol
 - FOUNDATION Fieldbus
 - PROFIBUS PA
 - PROFIBUS DP
 - Modbus RS485
 - Modbus TCP with Ethernet-APL
 - EtherNet/IP
 - PROFINET
 - PROFINET with Ethernet-APL
- Via service interface
 - CDI-RJ45 service interface
 - WLAN interface

Plain text display	With information on cause and remedial measures
1 ,	



Web browser

Plain text display	With information on cause and remedial measures
--------------------	---

Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes
	The following information is displayed depending on the device version: Supply voltage active Data transmission active Device alarm/error has occurred EtherNet/IP network available EtherNet/IP connection established PROFINET network available PROFINET connection established PROFINET blinking feature

Load

Output signal \rightarrow \blacksquare 16

Ex connection data

Safety-related values

Order code "Output; input 1"	Output type	Safety-related values "Output; input 1"	
		26 (+)	27 (-)
Option BA	Current output 4 to 20 mA HART	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option GA	PROFIBUS PA	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option LA	PROFIBUS DP	$U_{\rm N} = 32 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm AC}$	
Option MA	Modbus RS485	$U_{\rm N} = 30 \text{ V}_{\rm DC}$ $U_{\rm M} = 250 \text{ V}_{\rm AC}$	
Option MB	Modbus TCP with Ethernet-APL	$ \begin{array}{l} \text{APL port profile SLAX} \\ \text{SPE PoDL classes 10, 11, 12} \\ U_{N} = 30 \ V_{DC} \\ U_{M} = 250 \ V_{AC} \\ \end{array} $	2
Option SA	FOUNDATION Fieldbus	$U_{N} = 32 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option NA	EtherNet/IP	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option RA	PROFINET	$U_{N} = 30 V_{DC}$ $U_{M} = 250 V_{AC}$	
Option RB	PROFINET with Ethernet- APL	APL port profile SLAX SPE PoDL classes 10, 11, 12 U_N = 30 V_{DC} U_M = 250 V_{AC}	2

Order code	Output type	Safety-related values			
"Output; input 2"; "Output; input 3"		Output;	input 2	Output;	input 3
• / •		24 (+)	25 (-)	22 (+)	23 (-)
Option B	Current output 4 to 20 mA	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm Ad}$	С		
Option D	User-configurable input/ output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	С		
Option E	Pulse/frequency/switch output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	С		
Option F	Double pulse output	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	С		
Option H	Relay output	$U_{N} = 30 V_{DC}$ $I_{N} = 100 \text{ mA}_{DC}$ $U_{M} = 250 V_{AC}$			
Option I	Current input 4 to 20 mA	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm Ad}$	С		
Option J	Status input	$U_{\rm N} = 30 \ V_{\rm DC}$ $U_{\rm M} = 250 \ V_{\rm A0}$	С		_

Intrinsically safe values

Order code "Output; input 1"	Output type	Intrinsically safe values "Output; input 1"		
		26 (+) 27 (-)		
Option CA	Current output 4 to 20 mA HART Ex i passive	$\begin{split} &U_{i} = 30 \text{ V} \\ &I_{i} = 100 \text{ mA} \\ &P_{i} = 1.25 \text{ W} \\ &L_{i} = 0 \mu\text{H} \\ &C_{i} = 6 \text{ nF} \end{split}$		
Option CC	Current output 4 to 20 mA HART Ex i active	Ex ia $^{1)}$ $U_0 = 21.8 \text{ V}$ $I_0 = 90 \text{ mA}$ $P_0 = 491 \text{ mW}$ $L_0 = 4.1 \text{ mH (IIC)/15 mH}$ (IIB) $C_0 = 160 \text{ nF (IIC)/}$ 1160 nF (IIB)	Ex ic 2) $U_{0} = 21.8 \text{ V}$ $l_{0} = 90 \text{ mA}$ $P_{0} = 491 \text{ mW}$ $L_{0} = 9 \text{ mH (IIC)/39 mH (IIB)}$ $C_{0} = 600 \text{ nF (IIC)/}$ 4000 nF (IIB)	
		$\begin{split} &U_{i} = 30 \text{ V} \\ &I_{i} = 10 \text{ mA} \\ &P_{i} = 0.3 \text{ W} \\ &L_{i} = 5 \mu\text{H} \\ &C_{i} = 6 \text{ nF} \end{split}$		
Option HA	PROFIBUS PA Ex i (FISCO Field Device)	$Ex ia ^{1} \\ U_i = 30 V \\ l_i = 570 mA \\ P_i = 8.5 W \\ L_i = 10 \mu H \\ C_i = 5 nF$	Ex ic 2) $U_{i} = 32 \text{ V}$ $l_{i} = 570 \text{ mA}$ $P_{i} = 8.5 \text{ W}$ $L_{i} = 10 \mu\text{H}$ $C_{i} = 5 \text{ nF}$	
Option TA	FOUNDATION Fieldbus Ex i	$Ex ia^{1} \\ U_i = 30 \text{ V} \\ I_i = 570 \text{ mA} \\ P_i = 8.5 \text{ W} \\ L_i = 10 \mu\text{H} \\ C_i = 5 \text{ nF}$	Ex ic ²⁾ $U_i = 32 \text{ V}$ $l_i = 570 \text{ mA}$ $P_i = 8.5 \text{ W}$ $L_i = 10 \mu\text{H}$ $C_i = 5 \text{ nF}$	
Option RC	PROFINET with Ethernet-APL Ex i	Ex ia ¹⁾ 2-WISE power load APL port profile SLAA Ex ic ²⁾ 2-WISE power load APL port profile SLAC		

- Only available for Proline 500 transmitter Zone 1; Class I, Division 1. Only available for transmitter Zone 2; Class I, Division 2. 1)

Order code for	Output type	Intrinsically safe values or NIFW values			
"Output; input 2"; "Output; input 3"		Output;	input 2	Output;	input 3
		24 (+)	25 (-)	22 (+)	23 (-)
Option C	Current output 4 to 20 mA Ex i passive	$U_{i} = 30 \text{ V}$ $l_{i} = 100 \text{ mA}$ $P_{i} = 1.25 \text{ W}$ $L_{i} = 0$ $C_{i} = 0$			
Option G	Pulse/frequency/switch output Ex i passive	$\label{eq:Ui} \begin{aligned} &U_i = 30 \text{ V} \\ &l_i = 100 \text{ mA} \\ &P_i = 1.25 \text{ W} \\ &L_i = 0 \\ &C_i = 0 \end{aligned}$			

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

The outputs are galvanically isolated:
• from the power supply

- from one another
- from the potential equalization (PE) terminal

Protocol-specific data

HART

Manufacturer ID	0x11
Device type ID	0x3B
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω
System integration	Information on system integration: Operating Instructions → 🗎 130. ■ Measured variables via HART protocol ■ Burst Mode functionality

FOUNDATION Fieldbus

Manufacturer ID	0x452B48 (hex)
Ident number	0x103B (hex)
Device revision	1
DD revision	Information and files under:
CFF revision	www.endress.comwww.fieldcommgroup.org
Interoperability Test Kit (ITK)	Version 6.2.0
ITK Test Campaign Number	Information: www.endress.com www.fieldcommgroup.org
Link Master capability (LAS)	Yes
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device
Node address	Factory setting: 247 (0xF7)
Supported functions	The following methods are supported: Restart ENP Restart Diagnostic Set to OOS Set to AUTO Read trend data Read event logbook
Virtual Communication Relation	nships (VCRs)
Number of VCRs	44
Number of link objects in VFD	50
Permanent entries	1
Client VCRs	0
Server VCRs	10
Source VCRs	43
Sink VCRs	0
Subscriber VCRs	43
Publisher VCRs	43

Device Link Capabilities	
Slot time	4
Min. delay between PDU	8
Max. response delay	16
System integration	Information regarding system integration: Operating Instructions → 🗎 130. Cyclic data transmission Description of the modules Execution times Methods

PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x156F
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: ■ https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ https://www.profibus.com
Supported functions	Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Via operating tools (e.g. FieldCare)
Compatibility with earlier model	If the device is replaced, the measuring device Promass 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promass 300 GSD file. Previous model: Promass 83 PROFIBUS DP ■ ID No.: 1529 (hex) ■ Extended GSD file: EH3x1529.gsd ■ Standard GSD file: EH3_1529.gsd Description of the function scope of compatibility: Operating Instructions → 130.
System integration	Information regarding system integration: Operating Instructions → 🖺 130. Cyclic data transmission Block model Description of the modules

PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x156D
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: ■ https://www.endress.com/download On the device product page: PRODUCTS → Product Finder → Links ■ https://www.profibus.com

Supported functions	Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur			
Configuration of the device address	 DIP switches on the I/O electronics module Local display Via operating tools (e.g. FieldCare) 			
Compatibility with earlier model	If the device is replaced, the measuring device Promass 300 supports the compatibility of the cyclic data with previous models. It is not necessary to adjust the engineering parameters of the PROFIBUS network with the Promass 300 GSD file. Earlier models: Promass 80 PROFIBUS PA ID No.: 1528 (hex) Extended GSD file: EH3x1528.gsd Promass 83 PROFIBUS PA ID No.: 152A (hex) Extended GSD file: EH3x152A.gsd Standard GSD file: EH3x152A.gsd Description of the function scope of compatibility:			
System integration	Operating Instructions → 🗎 130. Information regarding system integration: Operating Instructions → 🖺 130. • Cyclic data transmission • Block model • Description of the modules			

Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1			
Response times	 Direct data access: typically 25 to 50 ms Auto-scan buffer (data range): typically 3 to 5 ms 			
Device type	Slave			
Slave address range	1 to 247			
Broadcast address range	0			
Function codes	 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers 			
Broadcast messages	Supported by the following function codes: O6: Write single registers 16: Write multiple registers 23: Read/write multiple registers			
Supported baud rate	 1200 BAUD 2400 BAUD 4800 BAUD 9600 BAUD 19200 BAUD 38400 BAUD 57600 BAUD 115200 BAUD 			
Data transmission mode	ASCII RTU			

Data access	Each device parameter can be accessed via Modbus RS485. For Modbus register information				
Compatibility with earlier model	If the device is replaced, the measuring device Promass 300 supports the compatibility of the Modbus registers for the process variables and the diagnostic information with the previous model Promass 83. It is not necessary to change the engineering parameters in the automation system. □ Description of the function scope of compatibility: Operating Instructions → ■ 130.				
System integration	Information regarding system integration: Operating Instructions → 🗎 130. ■ Modbus RS485 information ■ Function codes ■ Register information ■ Response time ■ Modbus data map				

EtherNet/IP

Protocol	 The CIP Networks Library Volume 1: Common Industrial Protocol The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP 				
Communication type	■ 10Base-T ■ 100Base-TX				
Device profile	Generic device (product type: 0x2B)				
Manufacturer ID	0x000049E				
Device type ID	0x103B				
Baud rates	Automatic ¹⁰ / ₁₀₀ Mbit with half-duplex and full-duplex detection				
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs				
Supported CIP connections	Max. 3 connections				
Explicit connections	Max. 6 connections				
I/O connections	Max. 6 connections (scanner)				
Configuration options for measuring device	 DIP switches on the electronics module for IP addressing Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser Electronic Data Sheet (EDS) integrated in the measuring device 				
Configuration of the EtherNet interface	 Speed: 10 MBit, 100 MBit, auto (factory setting) Duplex: half-duplex, full-duplex, auto (factory setting) 				
Configuration of the device address	 DIP switches on the electronics module for IP addressing (last octet) DHCP Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser EtherNet/IP tools, e.g. RSLinx (Rockwell Automation) 				
Device Level Ring (DLR)	Yes				
System integration	Information regarding system integration: Operating Instructions $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $				
	 Cyclic data transmission Block model Input and output groups 				

PROFINET

Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.3
Communication type	100 MBit/s

Conformance Class	Conformance Class B					
Netload Class	Netload Class 2 0 Mbps					
Baud rates	Automatic 100 Mbit/s with full-duplex detection					
Cycle times	From 8 ms					
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs					
Media Redundancy Protocol (MRP)	Yes					
System redundancy support	ystem redundancy S2 (2 AR with 1 NAP)					
Device profile	pplication interface identifier 0xF600 eneric device					
Manufacturer ID	0x11					
Device type ID	0x843B					
Device description files (GSD, DTM, DD)	nformation and files under: www.endress.com On the product page for the device: Documents/Software → Device drivers www.profibus.com					
Supported connections	 2 x AR (IO Controller AR) 1 x AR (IO-Supervisor Device AR connection allowed) 1 x Input CR (Communication Relation) 1 x Output CR (Communication Relation) 1 x Alarm CR (Communication Relation) 					
Configuration options for measuring device	 DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device. Onsite operation 					
Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server 					
Supported functions	 Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM) 					
System integration	Information regarding system integration: Operating Instructions → 🗎 130. Cyclic data transmission Overview and description of the modules Status coding Startup configuration Factory setting					

PROFINET with Ethernet-APL

Protocol	Application layer protocol for decentral device periphery and distributed automation, Version 2.43
Communication type	Ethernet Advanced Physical Layer 10BASE-T1L
Conformance Class	Conformance Class B (PA)
Netload Class	PROFINET Netload Robustness Class 2 10 Mbit/s

Baud rates	10 Mbit/s Full-duplex			
Cycle times	64 ms			
Polarity	Automatic correction of crossed "APL signal +" and "APL signal -" signal lines			
Media Redundancy Protocol (MRP)	Not possible (point-to-point connection to APL field switch)			
System redundancy support	System redundancy S2 (2 AR with 1 NAP)			
Device profile	PROFINET PA profile 4 (Application interface identifier API: 0x9700)			
Manufacturer ID	17			
Device type ID	0xA43B			
Device description files (GSD, DTM, FDI)	formation and files available at: www.endress.com → Downloads section www.profibus.com 2x AR (IO Controller AR) 2x AR (IO Supervisor Device AR connection allowed) DIP switches on the electronics module, for device name assignment (last part) Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of the measuring device.			
Supported connections	 2x AR (IO Controller AR) 2x AR (IO Supervisor Device AR connection allowed) 			
Configuration options for measuring device	 Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server via Web browser and IP address Device master file (GSD), can be read out via the integrated Web server of 			
Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol Asset management software (FieldCare, DeviceCare, Field Xpert) Integrated Web server 			
Supported functions	 Identification & Maintenance, simple device identifier via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the local display for simple device identification and assignment Device operation via asset management software (e.g. FieldCare, DeviceCare, SIMATIC PDM with FDI package) 			
System integration	Information regarding system integration: Operating Instructions $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $			
	 Cyclic data transmission Overview and description of the modules Status coding Factory setting 			

Power supply

Terminal assignment

Transmitter: supply voltage, input/outputs

HART

Supply voltage		Input/o	utput 1	Input/c	output 2	Input/c	output 3
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $					

FOUNDATION Fieldbus

Supply voltage		Input/o	utput 1	Input/o	utput 2	Input/o	utput 3	
1	L (+)	2 (-)	26 (A)	27 (B)	24 (+)	25 (-)	22 (+)	23 (-)
			The terminal assignment depends on the specific device version ordered $\Rightarrow \; riangleq \; 14.$					

PROFIBUS DP

Supply voltage		Input/o	utput 1	Input/o	utput 2	Input/o	utput 3
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $ ightarrow$ $ riangleq$ 14.					

PROFIBUS PA

Supply	voltage	Input/o	utput 1	Input/o	utput 2	Input/o	output 3
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $					

Modbus RS485

Supply	voltage	Input/o	output 1	Input/o	output 2	Input/o	output 3
1 (+)	2 (-)	26 (B)	27 (A)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $					

Modbus TCP with Ethernet-APL

Supply	voltage	Input/o	utput 1	Input/o	output 2	Input/o	output 3
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $					

PROFINET

Supply	voltage	Input/output 1	Input/output 2		Input/o	output 3
1 (+)	2 (-)	PROFINET (RJ45 connector)			22 (+) t depends on t rdered → 🗎 1	

PROFINET with Ethernet-APL

Supply	voltage	Input/o	utput 1	Input/o	output 2	Input/c	output 3
1 (+)	2 (-)	26 (+)	27 (-)	24 (+)	25 (-)	22 (+)	23 (-)
		The terminal assignment depends on the specific device version ordered → 🖺 14.					

EtherNet/IP

Supply	voltage	ge Input/output 1 Input/output 2		Input/output 3		
1 (+)	2 (-)	EtherNet/IP (RJ45 connector)		3	22 (+) t depends on t rdered → 🖺 1	*

Available device plugs

Povice plugs may not be used in hazardous areas!

Device plugs for fieldbus systems:

Order code for "Input; output 1"

- Option **SA** "FOUNDATION Fieldbus" → 🗎 34
- Option **GA** "PROFIBUS PA" → 🖺 34
- Option **NA** "EtherNet/IP" → 🖺 34
- Option **RA** "PROFINET" → 🖺 35
- Option **RB** "PROFINET with Ethernet-APL" → 🗎 35

Device plug for connecting to the service interface:

Order code for "Accessory mounted"

Option NB, RJ45 M12 adapter (service interface) → 🖺 48

Order code for "Input; output 1", option SA "FOUNDATION Fieldbus"

Order code for	Cable entry/con	nection → 🗎 36
"Electrical connection"	2	3
M, 3, 4, 5	7/8" connector	-

Order code for "Input; output 1", option GA "PROFIBUS PA"

Order code for	Cable entry/connection → 🖺 36		
"Electrical connection"	2	3	
L, N, P, U	Connector M12 × 1	-	

Order code for "Input; output 1", option NA "EtherNet/IP"

Order code for	Cable entry/connection → 🖺 36		
"Electrical connection"	2	3	
L, N, P, U	Connector M12 × 1	-	
R ¹⁾²⁾ , S ¹⁾²⁾ , T ¹⁾²⁾ , V ¹⁾²⁾	Connector M12 × 1	Connector M12 × 1	

- Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001
- 2) Suitable for integrating the device in a ring topology.

Order code for "Input; output 1", option RA "PROFINET"

Order code for	Cable entry/connection → 🖺 36		
"Electrical connection"	2	3	
L, N, P, U	Connector M12 × 1	_	
R ^{1) 2)} , S ^{1) 2)} , T ^{1) 2)} , V ^{1) 2)}	Connector M12 × 1	Connector M12 × 1	

- Cannot be combined with an external WLAN antenna (order code for "Enclosed accessories", option P8) of an RJ45 M12 adapter for the service interface (order code for "Accessories mounted", option NB) or of the remote display and operating module DKX001.
- 2) Suitable for integrating the device in a ring topology.

Order code for "Input; output 1", option RB "PROFINET with Ethernet-APL"

Order code	Cable entry/connection → 🗎 36		
"Electrical connection"	2	3	
L, N, P, U	M12 plug × 1	-	

Order code for "Accessory mounted", option NB "Adapter RJ45 M12 (service interface)"

Order code	Cable entry/coupling → 🖺 36	
"Accessory mounted"	Cable entry 2	Cable entry 3
NB	Plug M12 × 1	-

Supply voltage

Order code "Power supply"	Terminal voltage		Frequency range
Option D	DC 24 V	±20%	-
Option E	AC 100 to 240 V	-15+10%	50/60 Hz
Option I	DC 24 V	±20%	-
	AC 100 to 240 V	-15+10%	50/60 Hz

Power consumption

Transmitter

Max. 10 W (active power)

switch-on current	Max. 36 A (<5 ms) as per NAMUR Recommendation NE 21

Current consumption

Transmitter

- Max. 400 mA (24 V)
- Max. 200 mA (110 V, 50/60 Hz; 230 V, 50/60 Hz)

Power supply failure

- Totalizers stop at the last value measured.
- Depending on the device version, the configuration is retained in the device memory or in the pluggable data memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

Overcurrent protection element

The device must be operated with a dedicated circuit breaker, as it does not have an ON/OFF switch of its own.


- The circuit breaker must be easy to reach and labeled accordingly.
- Permitted nominal current of the circuit breaker: 2 A up to maximum 10 A.

Electrical connection

Transmitter connection




- Terminal assignment → 🖺 33
- Device plugs available → 🖺 34



A002678

- 1 Terminal connection for supply voltage
- 2 Terminal connection for signal transmission, input/output
- 3 Terminal connection for signal transmission, input/output or terminal for network connection via service interface (CDI-RJ45); Optional: terminal connection for external WLAN antenna or connection for remote display and operating module DKX001
- 4 Terminal connection for potential equalization (PE)
- An adapter for the RJ45 to the M12 plug is optionally available:
 Order code for "Accessories", option **NB**: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can therefore be established via an M12 plug without opening the device.




Connecting in a ring topology

Device versions with EtherNet/IP and PROFINET communication protocols can be integrated into a ring topology. The device is integrated via the terminal connection for signal transmission (output 1) and the connection to the service interface (CDI-RJ45).

- Integrate the transmitter into a ring topology:

 EtherNet/IP
 - PROFINET




A0026781

- 1 Terminal connection for supply voltage
- 2 Terminal connection for signal transmission: PROFINET or EtherNet/IP (RJ45 connector)
- 3 Terminal connection to service interface (CDI-RJ45)
- 4 Terminal connection for potential equalization (PE)

If the device has additional inputs/outputs, these are routed in parallel via the cable entry for connection to the service interface (CDI-RJ45).

Connecting the remote display and operating module DKX001

- i
- The remote display and operating module DKX001 is available as an optional extra $\rightarrow riangleq 127$..
- The remote display and operating module DKX001 is only available for the following housing versions, order code for "Housing":
 - Option A "Aluminum, coated"
 - Option L "Cast, stainless"
- The measuring instrument is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring instrument. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring instrument display module. Only one display or operation unit may be connected to the transmitter at any one time.




A0027518

- 1 Remote display and operating module DKX001
- 2 Terminal connection for potential equalization (PE)
- 3 Connecting cable
- 4 Measuring instrument
- 5 Terminal connection for potential equalization (PE)


Connection examples

Current output 4 to 20 mA HART



A0029055


- \blacksquare 2 Connection example for 4 to 20 mA HART current output (active)
- Automation system with current input (e.g. PLC)
- 2 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications → 48
- 3 Connection for HART operating devices $\rightarrow \blacksquare 109$
- 4 Resistor for HART communication ($\geq 250 \Omega$): observe maximum load $\Rightarrow = 16$
- 5 Analog display unit: observe maximum load $\rightarrow \blacksquare 16$
- 6 Transmitter



A002876

- 3 Connection example for 4 to 20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications → 🖺 48
- 4 Analog display unit: observe maximum load → 🖺 16
- 5 Transmitter


HART input



A002876

- 4 Connection example for HART input with a common negative (passive)
- 1 Automation system with HART output (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Ground cable shield at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 Analog display unit: observe maximum load $\rightarrow \blacksquare 16$
- 5 Pressure measuring device (e.g. Cerabar M, Cerabar S): observe requirements
- 6 Transmitter


PROFIBUS PA



■ 5 Connection example for PROFIBUS PA

- 1 Control system (e.g. PLC)
- 2 PROFIBUS PA segment coupler
- 3 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line

PROFIBUS DP




- \blacksquare 6 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2
- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter
- If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

Endress+Hauser 39

A0028768


EtherNet/IP



■ 7 Connection example for EtherNet/IP


- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter

EtherNet/IP: DLR (Device Level Ring)



- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 4 Transmitter
- 5 Connecting cable between the two transmitters


PROFINET



■ 8 Connection example for PROFINET


- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Device plug
- 5 Transmitter

PROFINET with Ethernet-APL




- **₽** 9 ${\it Connection example for PROFINET with Ethernet-APL}$
- 1 Cable shield
- 2 Measuring device
- 3 Local grounding
- Potential equalization
- 4 5 Trunk or TCP
- 6 Field switch

PROFINET: MRP (Media Redundancy Protocol)



- Control system (e.g. PLC)
- 2 Ethernet switch
- *Observe cable specifications* $\rightarrow \implies 49$
- Transmitter
- ${\it Connecting\ cable\ between\ the\ two\ transmitters}$


PROFINET: system redundancy S2



 \blacksquare 10 Connection example for system redundancy S2

- Control system 1 (e.g. PLC)
- Synchronization of control systems 2
- 3 Control system 2 (e.g. PLC)
- Industrial Ethernet Managed Switch 4
- Transmitter


FOUNDATION Fieldbus



Connection example for FOUNDATION Fieldbus **■** 11

- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus)
- 3 $\textit{Cable shield provided at one end. The cable shield must be grounded at both ends to comply with \textit{EMC} \\$ requirements; observe cable specifications
- T-box 4
- Measuring device Local grounding 5
- 6
- Bus terminator
- Potential matching line


Modbus RS485



 \blacksquare 12 Connection example for Modbus RS485, non-hazardous area and Zone 2; Class I, Division 2

- 1 Control system (e.g. PLC)
- 2 Cable shield provided at one end. The cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- 4 Transmitter

Modbus with TCP-APL




A0047536

© 13 Connection example for Modbus with TCP-APL


- 1 Cable shield
- 2 Measuring device
- 3 Local grounding
- 4 Potential equalization
- 5 Trunk or TCP
- 6 Field switch

Current output 4-20 mA



■ 14 Connection example for 4-20 mA current output (active)


- 1 Automation system with current input (e.g. PLC)
- 3 Transmitter



■ 15 Connection example for 4-20 mA current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- 3 Analog display unit: observe maximum load $\rightarrow \blacksquare 16$
- 4 Transmitter


Pulse/frequency output



■ 16 Connection example for pulse/frequency output (passive)

- Automation system with pulse/frequency input (e.g. PLC with 10 kΩ pull-up or pull-down resistor)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \blacksquare 19$


Switch output




Connection example for switch output (passive)

- Automation system with switch input (e.g. PLC with a 10 k Ω pull-up or pull-down resistor)

Double pulse output




- 18 Connection example for double pulse output (active)
- Automation system with double pulse input (e.g. PLC)
- 2
- 3 Double pulse output
- Double pulse output (slave), phase-shifted



A0029279

- **■** 19 Connection example for double pulse output (passive)
- Automation system with double pulse input (e.g. PLC with a 10 k Ω pull-up or pull-down resistor)
- 2 Power supply
- 3 Transmitter: observe input values $\rightarrow \implies 21$
- Double pulse output
- Double pulse output (slave), phase-shifted


Relay output



 \blacksquare 20 Connection example for relay output (passive)

- 1 Automation system with relay input (e.g. PLC)
- 2 Power supply


Current input



 \blacksquare 21 Connection example for 4 to 20 mA current input

- 1 Power supply
- 2 Terminal box
- 3 External measuring device (to read in pressure or temperature, for instance)
- 4 Transmitter

Status input



■ 22 Connection example for status input

- 1 Automation system with status output (e.g. PLC)
- 2 Power supply
- 3 Transmitter

Potential equalization

Requirements

For potential equalization:

- Pay attention to in-house grounding concepts
- Take account of operating conditions, such as the pipe material and grounding
- Connect the medium, sensor and transmitter to the same electric potential
- Use a ground cable with a minimum cross-section of 6 mm² (10 AWG) and a cable lug for potential equalization connections

Terminals

Spring-loaded terminals: Suitable for strands and strands with ferrules. Conductor cross-section 0.2 to 2.5 mm² (24 to 12 AWG).

Cable entries

- Cable gland: M20 × 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
 - NPT ½"
 - G ½"
 - M20
- Device plug for digital communication: M12 Only available for certain device versions $\rightarrow \blacksquare 34$.

Pin assignment, device plug

FOUNDATION Fieldbus

			Pin		Assignment	Coding	Plug/socket
2 -/-	()	3	1	+	Signal +	А	Plug
1-\(4	2	1	Signal –		
	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\		3		Grounding		
			4		Not assigned		

PROFIBUS PA


		Pin		Assignment	Coding	Plug/socket
2 /	3	1	+	PROFIBUS PA +	А	Plug
1	1 4 2			Grounding		
	7/	3	-	PROFIBUS PA -		
		4		Not assigned		



Recommended plug:

- Binder, series 713, part no. 99 1430 814 04
- Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

PROFINET





Recommended plug:

- Binder, series 825, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q

PROFINET with Ethernet-APL

	Pin	Assignment	Coding	Plug/socket
3 4	1	APL signal -	А	Socket
2 1	2	APL signal +		
	3	Cable shield ¹		
	4	Not used		
	Metal plug housing	Cable shield		
		¹ If a cable shield is used		

Recommended plug:

- Binder, series 713, part no. 99 1430 814 04
- Phoenix, part no. 1413934 SACC-FS-4QO SH PBPA SCO

EtherNet/IP


2	Pin		Assignment
	1	+	Tx
1 3	2	+	Rx
	3	-	Tx
	4	-	Rx
4 A0032047	Cod	ling	Plug/socket
	I)	Socket

Recommended plug:

- Binder, series 825, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q

Service interface for

Order code for "Accessories mounted", option NB: Adapter RJ45 M12 (service interface)



Recommended plug:

- Binder, series 825, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q

Cable specification

Permitted temperature range

- The installation guidelines that apply in the country of installation must be observed.
- The cables must be suitable for the minimum and maximum temperatures to be expected.

Power supply cable (incl. conductor for the inner ground terminal)

Standard installation cable is sufficient.

Protective grounding cable for the outer ground terminal

Conductor cross-section < 2.1 mm² (14 AWG)

The use of a cable lug enables the connection of larger cross-sections.

The grounding impedance must be less than 2 Ω .

Signal cable



For custody transfer, all signal lines must be shielded cables (tinned copper braiding, optical coverage \geq 85 %). The cable shield must be connected on both sides.

Current output 4 to 20 mA HART

Shielded twisted-pair cable.



See https://www.fieldcommgroup.org "HART PROTOCOL SPECIFICATIONS".

PROFIBUS PA

Shielded twisted-pair cable. Cable type A is recommended.



See https://www.profibus.com "PROFIBUS Installation Guidelines".

PROFIBUS DP

Shielded twisted-pair cable. Cable type A is recommended.



See https://www.profibus.com "PROFIBUS Installation Guidelines".

EtherNet/IP

Twisted-pair Ethernet CAT 5 or better.



See https://www.odva.org"EtherNet/IP Media Planning & Installation Manual".

PROFINET

Only PROFINET cables.



See https://www.profibus.com "PROFINET Planning guideline".

Ethernet-APL

Shielded twisted-pair cable. Cable type A is recommended.



See https://www.profibus.com Ethernet-APL White Paper "

FOUNDATION Fieldbus

Twisted, shielded two-wire cable.



For further information on planning and installing FOUNDATION Fieldbus networks see:

- Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)
- FOUNDATION Fieldbus Guideline
- IEC 61158-2 (MBP)

Modbus RS485

Shielded twisted-pair cable.



See https://modbus.org "MODBUS over Serial Line Specification and Implementation Guide".

Current output 0 /4 to 20 mA (excluding HART)

Standard installation cable is sufficient.

Pulse /frequency /switch output

Standard installation cable is sufficient.

Relay output

Standard installation cable is sufficient.

Current input 4 to 20 mA

Standard installation cable is sufficient.

Status input

Standard installation cable is sufficient.

Connecting cable for transmitter - remote display and operating module DKX001 $\,$

Standard cable

A standard cable can be used as the connecting cable.

Standard cable	4 cores (2 pairs); pair-stranded with common shield
Shielding	Tin-plated copper-braid, optical cover \geq 85 %
Capacitance: core/shield	Maximum 1000 nF for Zone 1; Class I, Division 1
L/R	Maximum 24 μ H/ Ω for Zone 1; Class I, Division 1
Cable length	Maximum 300 m (1000 ft), see the following table

Cross-section	Cable length for use in: Non-hazardous area Hazardous area: Zone 2; Class I, Division 2 Hazardous area: Zone 1; Class I, Division 1	
0.34 mm ² (22 AWG)	80 m (270 ft)	
0.50 mm ² (20 AWG)	120 m (400 ft)	
0.75 mm ² (18 AWG)	180 m (600 ft)	
1.00 mm ² (17 AWG)	240 m (800 ft)	
1.50 mm ² (15 AWG)	300 m (1000 ft)	

Optionally available connecting cable

Standard cable	$2\times2\times0.34~\text{mm}^2$ (22 AWG) PVC cable $^{1)}$ with common shield (2 pairs, pair-stranded)		
Flame resistance	According to DIN EN 60332-1-2		
Oil-resistance	According to DIN EN 60811-2-1		
Shielding	Tin-plated copper-braid, optical cover ≥ 85 %		
Capacitance: core/shield	<200 pF/m		
L/R	<24 μΗ/Ω		
Available cable length	10 m (35 ft)		
Operating temperature	When mounted in a fixed position: -50 to $+105$ °C (-58 to $+221$ °F); when cable can move freely: -25 to $+105$ °C (-13 to $+221$ °F)		

1) UV radiation can impair the cable outer sheath. Protect the cable from direct sunshine where possible.


Overvoltage protection

Mains voltage fluctuations	→ 🖺 35
Overvoltage category	Overvoltage category II
Short-term, temporary overvoltage	Between cable and ground up to 1200 V, for max. 5 s
Long-term, temporary overvoltage	Between cable and ground up to 500 V

Performance characteristics

Reference operating conditions

- Error limits based on ISO 11631
- Water
 - +15 to +45 °C (+59 to +113 °F)
 - 2 to 6 bar (29 to 87 psi)
- Data as indicated in the calibration protocol
- Accuracy based on accredited calibration rigs according to ISO 17025



Maximum measurement error

o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$; T = medium temperature

Base accuracy



Design fundamentals → 🖺 55

Mass flow and volume flow (liquids)

- ±0.05 % o.r. (optional for mass flow: PremiumCal; order code for "Calibration flow", option D)
- ±0.10 % o.r. (standard)

Mass flow (gases)

±0.25 % o.r.

Mass flow (cryogenic liquids and gases under −100 $^{\circ}$ C (−148 $^{\circ}$ F))

±0.35 % o.r. (order code for "Measuring tube material", option LA)

Density (liquids)

Under reference conditions	Standard density calibration	Wide-range Density specification ^{1) 2)}	Extended density calibration ^{3) 4)}
[g/cm³]	[g/cm³]	[g/cm³]	[g/cm³]
±0.0005	±0.0005	±0.001	±0.0005

- 1) Valid range for special density calibration: 0 to 2 g/cm³, +5 to +80 $^{\circ}$ C (+41 to +176 $^{\circ}$ F)
- order code for "Application package", option EE "Special density" (for nominal diameter ≤ 100 DN)
- 3) Valid range for extended density calibration: 0 to 2 g/cm^3 , +20 to +60 °C (+68 to +140 °F)
- 4) order code for "Application package", option E1 "Extended density"

Density (cryogenic liquids and gases under −100 °C (−148 °F))

±0.05 g/cm³ (order code for "Measuring tube material", option LA)

Temperature

 $\pm 0.5 \,^{\circ}\text{C} \pm 0.005 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.9 \,^{\circ}\text{F} \pm 0.003 \cdot (\text{T} - 32) \,^{\circ}\text{F})$

Zero point stability

D	N	Zero point stability		
[mm]	[in]	[kg/h]	[lb/min]	
8	3/8	0.030	0.001	
15	1/2	0.200	0.007	
25	1	0.540	0.019	
40	1½	2.25	0.083	
50	2	3.50	0.129	

D	N	Zero point stability		
[mm]	[in]	[kg/h]	[lb/min]	
80	3	9.0	0.330	
100	4	14.0	0.514	
150	6	32.0	1.17	
250	10	88.0	3.23	

High-temperature version: order code for "Measuring tube material", option TS, TT, TU

D	N	Zero poin	t stability
[mm]	[in]	[kg/h]	[lb/min]
15	1/2	0.3	0.011
25	1	1.8	0.0662
50	2	7	0.2573
80	3	18	0.6615
100	4	21	0.7718
150	6	48	1.764
250	10	132	4.851

For devices with low-temperature version, order code for "Measuring tube mat., wetted surface", option LA, please note the following:

NOTICE

Zero point confirmation and zero adjustment are difficult to carry out in the field due to the vaporization of the cryogenic liquid.

► As a general rule, the factory-set zero point should not be changed. Please ensure that the medium is in the liquid phase if a zero adjustment is to be carried out.

Flow values

Flow values as turndown parameters depending on nominal diameter.

SI units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[mm]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]
8	2 000	200	100	40	20	4
15	6500	650	325	130	65	13
25	18000	1800	900	360	180	36
40	45 000	4500	2 2 5 0	900	450	90
50	70 000	7 000	3 500	1400	700	140
80	180 000	18000	9000	3 600	1800	360
100	350000	35 000	17 500	7 000	3 500	700
150	800000	80 000	40 000	16000	8000	1600
250	2 200 000	220 000	110 000	44000	22 000	4400

52

US units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[inch]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]
3/8	73.50	7.350	3.675	1.470	0.735	0.147
1/2	238.9	23.89	11.95	4.778	2.389	0.478
1	661.5	66.15	33.08	13.23	6.615	1.323
1½	1654	165.4	82.70	33.08	16.54	3.308
2	2 5 7 3	257.3	128.7	51.46	25.73	5.146
3	6615	661.5	330.8	132.3	66.15	13.23
4	12860	1286	643.0	257.2	128.6	25.72
6	29 400	2 940	1470	588	294	58.80
10	80850	8085	4043	1617	808.5	161.7

Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

[.	Accuracy	±5 μA
- 1		

Pulse/frequency output

o.r. = of reading

Repeatability

o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$; T = medium temperature

Base repeatability



Design fundamentals → 🖺 55

Mass flow and volume flow (liquids)

±0.025 % o.r. (PremiumCal)

±0.05 % o.r.

Mass flow (gases)

±0.20 % o.r.

Mass flow (cryogenic liquids and gases under $-100 \,^{\circ}\mathrm{C}$ ($-148 \,^{\circ}\mathrm{F}$))

 ± 0.175 % % o.r. (order code for "Measuring tube material", option LA)

Density (liquids)

 $\pm 0.00025 \text{ g/cm}^3$

Density (cryogenic liquids and gases under −100 °C (−148 °F))

 ± 0.025 g/cm³ (order code for "Measuring tube material", option LA)

Temperature

 $\pm 0.25 \,^{\circ}\text{C} \pm 0.0025 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.45 \,^{\circ}\text{F} \pm 0.0015 \cdot (\text{T}-32) \,^{\circ}\text{F})$

Response time

The response time depends on the configuration (damping).

Influence of ambient temperature

Current output

Temperature coefficient	Max. 1 μΑ/°C
-------------------------	--------------

Pulse/frequency output

Temperature coefficient	No additional effect. Included in accuracy.
-------------------------	---

Influence of medium temperature

Mass flow

o.f.s. = of full scale value

If there is a difference between the temperature during zero adjustment and the process temperature, the additional measurement error of the sensors is typically ±0.0002 %o.f.s./°C (±0.0001 % o. f.s./°F).

The influence is reduced when the zero adjustment is performed at process temperature.

If there is a difference between the density calibration temperature and the process temperature, the measurement error of the sensors is typically ± 0.00005 q/cm³/°C (± 0.000025 q/cm³/°F). Field density adjustment is possible.


Can also be used for order code for "Measuring tube material", option LA up to $-100 \,^{\circ}$ C ($-148 \,^{\circ}$ F).

Wide-range density specification (special density calibration)

If the process temperature is outside the valid range ($\Rightarrow \implies 51$) the measurement error is $\pm 0.00005 \text{ g/cm}^3 / ^{\circ}\text{C} (\pm 0.000025 \text{ g/cm}^3 / ^{\circ}\text{F})$

Extended density specification

If the process temperature is outside the valid range ($\Rightarrow \equiv 51$) the measurement error is $\pm 0.000025 \text{ g/cm}^3 \text{ /°C } (\pm 0.0000125 \text{ g/cm}^3 \text{ /°F})$



- Field density adjustment, for example at +20 °C (+68 °F)
- Special density calibration 2
- Applicable for the order code for "Measuring tube material", option LA
- Extended density calibration

Temperature

 $\pm 0.005 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.005 \cdot (\text{T} - 32) \,^{\circ}\text{F})$

Influence of medium pressure

The following shows how the process pressure (gauge pressure) affects the accuracy of the mass flow.

o.r. = of reading

i

It is possible to compensate for the effect by:

- Reading in the current pressure measured value via the current input or a digital input.
- Specifying a fixed value for the pressure in the device parameters.

Operating Instructions $\rightarrow \blacksquare 130$.

DN		[% o.r./bar]	[% o.r./psi]
[mm]	[in]		
8	3/8	no influer	nce
15	1/2	-0.002	-0.0001
25	1	no influence	
40	11/2	-0.003	-0.0002
50	2	-0.008	-0.0006
80	3	-0.009	-0.0006
100	4	-0.007	-0.0005
150	6	-0.009	-0.0006
250	10	-0.009	-0.0006

Design fundamentals

o.r. = of reading, o.f.s. = of full scale value

BaseAccu = base accuracy in % o.r., BaseRepeat = base repeatability in % o.r.

MeasValue = measured value; ZeroPoint = zero point stability


Calculation of the maximum measured error as a function of the flow rate

Flow rate	Maximum measured error in % o.r.
$\geq \frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$	± BaseAccu
A0021332	Augusti
< ZeroPoint BaseAccu · 100	± ZeroPoint MeasValue · 100
A0021333	A0021334

Calculation of the maximum repeatability as a function of the flow rate

Flow rate	Maximum repeatability in % o.r.
$\geq \frac{\frac{1}{2} \cdot \text{ZeroPoint}}{\text{BaseRepeat}} \cdot 100$	± BaseRepeat
A0021335	
$<\frac{\frac{1}{2} \cdot ZeroPoint}{BaseRepeat} \cdot 100$	$\pm \frac{1}{2} \cdot \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$
A0021336	A0021337


Example of maximum measurement error



- E Maximum measurement error in % o.r. (example with PremiumCal)
- Q Flow rate in % of maximum full scale value

Mounting

Installation point




A00287

To prevent measuring errors arising from accumulation of gas bubbles in the measuring pipe, avoid the following mounting locations in the piping:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

Installation in down pipes

However, the following installation suggestion allows for installation in an open vertical pipeline. Pipe restrictions or the use of an orifice with a smaller cross-section than the nominal diameter prevent the sensor running empty while measurement is in progress.



Installation in a down pipe (e.g. for batching applications)

- Supply tank
- Sensor
- 2 3 4 Orifice plate, pipe restriction
- Valve
- Filling vessel

D	N	Ø orifice plate, pipe restriction		
[mm]	[in]	[mm]	[in]	
8	3/8	6	0.24	
15	1/2	10	0.40	
25	1	14	0.55	
40	1 ½	22	0.87	
50	2	28	1.10	
80	3	50	1.97	
100	4	65	2.60	
150	6	90	3.54	
250	10	150	5.91	

Orientation


The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

	Orientation				
A	Vertical orientation	A0015591	✓ ✓ 1)		
В	Horizontal orientation, transmitter at top	A0015589	✓ ✓ ²⁾ Exception: → • 24, • 58		

	Recommendation		
С	Horizontal orientation, transmitter at bottom	A0015590	✓✓ ³⁾ Exception: → ② 24, ③ 58
D	Horizontal orientation, transmitter at side	A0015592	×

- 1) This orientation is recommended to ensure self-draining.
- 2) Applications with low process temperatures may reduce the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.
- 3) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.

If a sensor is installed horizontally with a curved measuring tube, match the position of the sensor to the fluid properties.



A00287

- 24 Orientation of sensor with curved measuring tube
- 1 Avoid this orientation for fluids with entrained solids: Risk of solids accumulating
- 2 Avoid this orientation for outgassing fluids: Risk of gas accumulating

Inlet and outlet runs

Special mounting instructions

Drainability

When installed vertically, the measuring tubes can be drained completely and protected against buildup.

Hygienic compatibility



- In the case of measuring devices with the order code for "Housing", option B "Stainless, hygienic", to seal the connection compartment cover, screw it closed finger-tight and tighten it by another 45° (corresponds to 15 Nm).

Rupture disk

WARNING

Danger from medium escaping!

Medium escaping under pressure can cause injury or material damage.


- ► Take precautions to prevent danger to persons and damage if the rupture disk is actuated.
- lacktriangle Observe the information on the rupture disk sticker.
- Make sure that the function and operation of the rupture disk is not impeded through the installation of the device.
- Do not use a heating jacket.
- ▶ Do not remove or damage the rupture disk.

The position of the rupture disk is indicated by a sticker affixed beside it.

The transportation guard must be removed.

The existing connecting nozzles are not intended for the purpose of rinsing or pressure monitoring, but instead serve as the mounting location for the rupture disk.

In the event of a failure of the rupture disk, a drain device can be screwed onto the internal thread of the rupture disk in order to drain off any escaping medium.



- Rupture disk label
- 2 Rupture disk with 1/2" NPT internal thread and 1" width across flats
- 3 Transportation guard

For information on the dimensions, see the "Mechanical construction" section (accessories).

Zero verification and zero adjustment

Experience shows that zero adjustment is advisable only in special cases:

- To achieve maximum measurement accuracy even with low flow rates.
- Under extreme process or operating conditions (e.g. very high process temperatures or very highviscosity fluids).
- For gas applications with low pressure

For information on checking the zero point and performing a zero adjustment, see the Operating Instructions for the device.

To achieve the highest possible measurement accuracy at low flow rates, the installation must protect the sensor from mechanical stresses during operation.

Environment

Ambient temperature range

Measuring device	 -40 to +60 °C (-40 to +140 °F) Order code for "Test, certificate", option JP: -50 to +60 °C (-58 to +140 °F)
Readability of the local display	-20 to $+60$ °C (-4 to $+140$ °F) The readability of the display may be impaired at temperatures outside the temperature range.

Parameter Dependency of ambient temperature on medium temperature ightarrow $\stackrel{ ext{ iny }}{=}$ 61

•	If operating	outdoors:
---	--------------	-----------

Avoid direct sunlight, particularly in warm climatic regions.

Storage temperature								
Climate class	DIN EN 60068-2-38 (test Z/AD)							
Relative humidity	The device is suitable for use outdoors and indoors with a relative humidity of 4 to 95 %.							
Operating height	According to EN 61010-1 $\bullet \le 2000\mathrm{m}$ (6562 ft) $\bullet > 2000\mathrm{m}$ (6562 ft) with additional overvoltage protection (e.g. Endress+Hauser HAW Series)							
Degree of protection	Transmitter							
	 IP66/67, Type 4X enclosure, suitable for pollution degree 4 When the housing is open: IP20, Type 1 enclosure, suitable for pollution degree 2 Display module: IP20, Type 1 enclosure, suitable for pollution degree 2 							
	Optional							
	Order code for "Sensor options", option CM "IP69"							
	External WLAN antenna							
	IP67							
hock and vibration esistance	Vibration sinusoidal, in accordance with IEC 60068-2-6 2 to 8.4 Hz, 3.5 mm peak 8.4 to 2 000 Hz, 1 g peak							
	Vibration broad-band random, according to IEC 60068-2-64							
	 10 to 200 Hz, 0.003 g²/Hz 200 to 2000 Hz, 0.001 g²/Hz Total: 1.54 g rms 							
	Shock half-sine, according to IEC 60068-2-27							
	6 ms 30 g							
	Rough handling shocks according to IEC 60068-2-31							
Internal cleaning	CIP cleaningSIP cleaning							
	 Options Oil- and grease-free version for wetted parts, without declaration Order code for "Service", option HA ¹⁾ Oil- and grease-free version for wetted parts as per IEC/TR 60877-2.0 and BOC 50000810-4, with declaration Order code for "Service", option HB ¹⁾ 							
Mechanical load	Transmitter housing: Protect against mechanical effects, such as shock or impact Do not use as a ladder or climbing aid							

¹⁾ The cleaning refers to the measuring instrument only. Any accessories supplied are not cleaned.

Electromagnetic compatibility (EMC)

- As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)
- As per IEC/EN 61000-6-2 and IEC/EN 61000-6-4
- Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170
 Volume 2, IEC 61784
- The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.
- Details are provided in the Declaration of Conformity.
- This unit is not intended for use in residential environments and cannot guarantee adequate protection of the radio reception in such environments.

Process

Medium temperature range

Standard version	-50 to +150 °C (-58 to +302 °F)	Order code for "Measuring tube mat., wetted surface", option HA, SA, SB, SC
Extended temperature version	-50 to +240 °C (-58 to +464 °F)	Order code for "Measuring tube mat., wetted surface", option SD, SE, SF, TH
High-temperature version	−50 to +350 °C (−58 to +662 °F)	For nominal diameters DN 15 (½"), 25 (1"), 50 to 250 (2 to 10") Order code for "Measuring tube mat., wetted surface", option TS, TT, TU
Low-temperature version	-196 to +150 °C (-320 to +302 °F) NOTICE Material fatigue due to excessive temperature difference! ► Maximum temperature difference of media used: 300 K	Order code for "Measuring tube mat., wetted surface", option LA


Pressure-temperature ratings

The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.




- Pressure-temperature ratings with the +151 to +240 °C (+304 to +464 °F) temperature range only for the extended temperature version of the measuring device.
- Pressure-temperature ratings with the +241 to +350 °C (+466 to +662 °F) temperature range only for the high-temperature version of the measuring device.
- Pressure-temperature ratings with the -196 to +150 °C (-320 to +302 °F) temperature range only for the low-temperature version of the measuring device.

Flange similar to EN 1092-1 (DIN 2501)




■ 25 With flange material 1.4404 (F316/F316L), Alloy C22

Flange similar to ASME B16.5




■ 26 With flange material 1.4404 (F316/F316L)




■ 27 With flange material Alloy C22

Flange JIS B2220




 \blacksquare 28 With flange material 1.4404 (F316/F316L), Alloy C22

Flange DIN 11864-2 Form A




■ 29 With connection material 1.4404 (316/316L)

Lap joint flange according to EN 1092-1 (DIN 2501)




■ 30 With flange material 1.4301 (F304); wetted parts Alloy C22

Lap joint flange according to ASME B16.5




■ 31 With flange material 1.4301 (F304); wetted parts Alloy C22

Lap joint flange JIS B2220



32 € With flange material 1.4301 (F304); wetted parts Alloy C22


Thread DIN 11851



№ 33 With connection material 1.4404 (316/316L)


DIN 11851 allows for applications up to +140 $^{\circ}\text{C}$ (+284 $^{\circ}\text{F}) if suitable sealing materials are used.$ Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

Thread DIN 11864-1 Form A




₹ 34 With connection material 1.4404 (316/316L)

Thread ISO 2853



■ 35 With connection material 1.4404 (316/316L)


Thread SMS 1145



■ 36 With connection material 1.4404 (316/316L)


SMS 1145 allows for applications up to 16 bar (232 psi) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

VCO



■ 37 With connection material 1.4404 (316/316L)

Tri-Clamp




A0032216-EI

The clamp connections are suitable up to a maximum pressure of 16 bar (232 psi). Please observe the operating limits of the clamp and seal used as they can be over 16 bar (232 psi). The clamp and seal are not included in the scope of supply.

Sensor housing

For standard versions with the temperature range -50 to +150 °C (-58 to +302 °F), the sensor housing is filled with dry nitrogen gas and protects the electronics and mechanics inside.

For all other temperature versions the sensor housing is filled with dry inert gas.



fluid will initially be contained by the sensor housing.

In the event of a tube failure, the pressure level inside the sensor housing will rise according to the operating process pressure. If the user judges that the sensor housing burst pressure does not provide an adequate safety margin, the device can be fitted with a rupture disk. This prevents excessively high pressure from forming inside the sensor housing. Therefore, the use of a rupture disk is strongly recommended in applications involving high gas pressures, and particularly in

applications in which the process pressure is greater than 2/3 of the sensor housing burst pressure.

If the sensor is to be purged with gas (gas detection), it should be equipped with purge connections.



Do not open the purge connections unless the containment can be filled immediately with a dry, inert gas. Use only low pressure to purge.

Maximum pressure:

- DN 08 to 150 (3/8 to 6"): 5 bar (72.5 psi)
- DN 250 (10"):
 - Medium temperature ≤ 100 °C (212 °F): 5 bar (72.5 psi)
 - Medium temperature > 100 °C (212 °F): 3 bar (43.5 psi)

Burst pressure of the sensor housing

The following sensor housing burst pressures are only valid for standard devices and/or devices equipped with closed purge connections (not opened/as delivered).

If a device fitted with purge connections (order code for "Sensor option", option CH "Purge connection") is connected to the purge system, the maximum pressure is determined by the purge system itself or by the device, depending on which component has the lower pressure classification.

If the device is fitted with a rupture disk (order code for "Sensor option", option CA "Rupture disk"), the rupture disk trigger pressure is decisive .

The sensor housing burst pressure refers to a typical internal pressure which is reached prior to mechanical failure of the sensor housing and which was determined during type testing. The

corresponding type test declaration can be ordered with the device (order code for "Additional approval", option LN "Sensor housing burst pressure, type test").

D	N	Sensor housing	burst pressure
[mm]	[in]	[bar]	[psi]
8	3/8	400	5800
15	1/2	350	5070
25	1	280	4060
40	11/2	260	3770
50	2	180	2610
80	3	120	1740
100	4	95	1370
150	6	75	1080
250	10	50	720

For information on the dimensions: see the "Mechanical construction" section

Rupture disk


To increase the level of safety, a device version with a rupture disk with a trigger pressure of 10 to 15 bar (145 to 217.5 psi)can be used (order code for "Sensor option", option CA "rupture disk").

The use of rupture disks cannot be combined with the separately available heating jacket.

For information on the dimensions: see the "Mechanical construction" section (accessories) → 🖺 89

Flow limit

Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.



- The minimum recommended full scale value is approx. 1/20 of the maximum full scale value
- In most applications, 20 to 50 % of the maximum full scale value can be considered ideal
- A low full scale value must be selected for abrasive media (such as liquids with entrained solids): flow velocity < 1 m/s (< 3 ft/s).
- For gas measurement the following rules apply:
 - The flow velocity in the measuring tubes should not exceed half the sound velocity (0.5 Mach).
 - The maximum mass flow depends on the density of the gas: formula

Pressure loss


Promass F with reduced pressure loss: order code for "Sensor option", option CE "Reduced pressure loss" $\,$

Static pressure

It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas. This is prevented by means of a sufficiently high static pressure.

For this reason, the following mounting locations are recommended:

- At the lowest point in a vertical pipe
- Downstream from pumps (no danger of vacuum)



A0028777

Thermal insulation

In the case of some fluids, it is important to keep the heat radiated from the sensor to the transmitter to a low level. A wide range of materials can be used for the required insulation.


The following device versions are recommended for versions with thermal insulation:

- Version with extended neck for insulation:
 - Order code for "Sensor option", option CG with an extended neck length of 105 mm (4.13 in).
- Extended temperature version:
 - Order code for "Measuring tube material", option SD, SE, SF or TH with an extended neck length of 105 mm (4.13 in).
- High-temperature version:
 - Order code for "Measuring tube material", option TS, TT or TU with an extended neck length of 142 mm (5.59 in).

NOTICE

Electronics overheating on account of thermal insulation!

- Recommended orientation: horizontal orientation, transmitter housing pointing downwards.
- Do not insulate the transmitter housing.
- Maximum permissible temperature at the lower end of the transmitter housing: $80 \, ^{\circ}\text{C}$ (176 $^{\circ}\text{F}$)
- Regarding thermal insulation with an exposed extended neck: We advise against insulating the extended neck to ensure optimal heat dissipation.



A003439

■ 38 Thermal insulation with exposed extended neck



Low-temperature version: It is generally not necessary to insulate the transmitter housing . If insulation is provided, the rules that apply are the same as those for thermal insulation.

Heating

Some fluids require suitable measures to avoid loss of heat at the sensor.

Heating options

- Electrical heating, e.g. with electric band heaters ²⁾
- Via pipes carrying hot water or steam
- Via heating jackets



NOTICE

Danger of overheating when heating

- Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F).
- Ensure that sufficient convection takes place at the transmitter neck.
- Ensure that a sufficiently large area of the transmitter neck remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.
- When using in potentially explosive atmospheres, observe the information in the device-specific Ex documentation. For detailed information on the temperature tables, see the separate document entitled "Safety Instructions" (XA) for the device.
- Consider the "830 ambient temperature too high" and "832 electronics temperature too high" process diagnostics if overheating cannot be ruled out based on a suitable system design.

Vibrations

The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by plant vibrations.

²⁾ The use of parallel electric band heaters is generally recommended (bidirectional electricity flow). Particular considerations must be made if a single-wire heating cable is to be used. Additional information is provided in the document EA01339D "Installation instructions for electrical trace heating systems" → 🖺 132

Custody transfer

The measuring device is optionally tested in accordance with OIML R117/R81 and has an EU type evaluation certificate which authorizes the use in EU type-examination certificates according to Measuring Instruments Directive 2014/32/EU for service subject to legal metrological control ("custody transfer") for liquids other than water and cryogenic liquids (Annex VII).

The measuring device is optionally tested according to OIML R137 and has an EU type-examination certificate according to Measuring Instruments Directive 2014/32/EU for service subject to legal metrological control ("custody transfer") as a gas meter (Annex IV).

The device is used with a legally controlled totalizer display on the local display and optionally with outputs subject to legal metrological control.

Measuring devices subject to legal metrological control totalize in both directions, i.e. all the outputs consider flow components in the positive (forward) and negative (reverse) flow direction.

Generally a measuring device subject to legal metrological control is secured against tampering by seals on the transmitter or sensor. These seals may normally only be opened by a representative of the competent authority for legal metrology controls.

After putting the device into circulation or after sealing the device, operation is only possible to a limited extent.

Detailed ordering information is available from your local Endress+Hauser sales center for national approvals, which are based on the OIML certificates, for applications with liquids other than water, cryogenic liquids or gases.




More information is provided in the supplementary documentation.

Mechanical construction

Dimensions in SI units

Compact version



A0033786

Order code for "Housing", option A "Aluminum, coated"

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F ²⁾³⁾	G 4)	Н	I 4)	K	L	M
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
8	169	68	101	75	259.5	334.5	200	59	141	5.35	5)	70
15	169	68	101	75	259.5	334.5	200	59	141	8.31	5)	70
25	169	68	101	75 ⁶⁾	259.5	334.5	200	59	141	12.0	5)	70
40	169	68	101	105	264.5	369.5	200	59	141	17.6	5)	79
50	169	68	101	141	274.5	415.5	200	59	141	26.0	5)	99
80	169	68	101	200	294.5	494.5	200	59	141	40.5	5)	139
100	169	68	101	254	312.5	566.5	200	59	141	51.2	5)	176
150	169	68	101	378	333.5	711.5	200	59	141	68.9	5)	218
250	169	68	101	548	377.5	925.5	200	59	141	102.3	5)	305

- Depending on the cable gland used: values up to +30 mm
- 2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +70 mm
- 3) With order code for "Measuring tube material", option TS, TT, TU: values $\pm 102 \text{ mm}$
- 4) For version without local display: values 30 mm
- 5) Depending on the process connection
- 6) With order code for "Measuring tube material", option TT, TU: value +25 mm

Order code for "Housing", option A "Aluminum, coated"; Ex d

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G 4)	Н	I 4)	K	L	M
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
8	188	85	103	75	260.5	335.5	217	58	159	5.35	5)	70
15	188	85	103	75	260.5	335.5	217	58	159	8.31	5)	70
25	188	85	103	75 ⁶⁾	260.5	335.5	217	58	159	12.0	5)	70
40	188	85	103	105	265	370	217	58	159	17.6	5)	79
50	188	85	103	141	275	416	217	58	159	26.0	5)	99
80	188	85	103	200	295	495	217	58	159	40.5	5)	139
100	188	85	103	254	313.5	567.5	217	58	159	51.2	5)	176

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G ⁴⁾	Н	I 4)	К	L	M
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
150	188	85	103	378	334.5	712.5	217	58	159	68.9	5)	218
250	188	85	103	548	378	926	217	58	159	102.3	5)	305

- 1) Depending on the cable gland used: values up to + 30 mm
- 2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +70 mm
- 3) With order code for "Measuring tube material", option TS, TT, TU: values +102 mm
- 4) For version without local display: values 40 mm
- 5) Depending on the process connection
- 6) With order code for "Measuring tube material", option TT, TU: value +25 mm

Order code for "Housing", option B "Stainless, hygienic"

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G ⁴⁾	Н	I 4)	K	L	M
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
8	183	73	110	75	259.5	334.5	200	65	135	5.35	5)	70
15	183	73	110	75	259.5	334.5	200	65	135	8.31	5)	70
25	183	73	110	75 ⁶⁾	259.5	334.5	200	65	135	12.0	5)	70
40	183	73	110	105	264.5	369.5	200	65	135	17.6	5)	79
50	183	73	110	141	274.5	415.5	200	65	135	26.0	5)	99
80	183	73	110	200	294.5	494.5	200	65	135	40.5	5)	139
100	183	73	110	254	312.5	566.5	200	65	135	51.2	5)	176
150	183	73	110	378	333.5	711.5	200	65	135	68.9	5)	218
250	183	73	110	548	377.5	925.5	200	65	135	102.3	5)	305

- 1) Depending on the cable gland used: values up to +30 mm
- 2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +70 mm
- 3) With order code for "Measuring tube material", option TS, TT, TU: values $\pm 102 \text{ mm}$
- 4) For version without local display: values 13 mm
- 5) Depending on the process connection
- 6) With order code for "Measuring tube material", option TT, TU: value +25 mm

Order code for "Housing", option L "Cast, stainless"


DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G	Н	I	K	L	М
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
8	186	85	101	75	260	335	217	60	157	5.35	4)	70
15	186	85	101	75	260	335	217	60	157	8.31	4)	70
25	186	85	101	75 ⁵⁾	260	335	217	60	157	12.0	4)	70
40	186	85	101	105	264.5	369.5	217	60	157	17.6	4)	79
50	186	85	101	141	274.5	415.5	217	60	157	26.0	4)	99
80	186	85	101	200	294.5	494.5	217	60	157	40.5	4)	139
100	186	85	101	254	313	567	217	60	157	51.2	4)	176

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G	Н	I	K	L	M
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
150	186	85	101	378	334	712	217	60	157	68.9	4)	218
250	186	85	101	548	377.5	925.5	217	60	157	102.3	4)	305

- 1) Depending on the cable gland used: values up to \pm 30 mm
- 2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +70 mm
- 3) With order code for "Measuring tube material", option TS, TT, TU: values +102 mm
- 4) Depending on the process connection
- 5) With order code for "Measuring tube material", option TT, TU: value +25 mm

Flange connections

Fixed flange EN 1092-1, ASME B16.5, JIS B2220



A001562



Length tolerance for dimension L in mm:

- DN \leq 100: +1.5/-2.0
- DN ≥ 150: ±3.5

Flange similar to EN 1092-1 (DIN 2501): PN16

1.4404 (F316/F316L): order code for "Process connection", option D1S

Alloy C22: order code for "Process connection", option D1C

Flange with groove similar to EN 1092-1 Form D (DIN 2512N): PN16

1.4404 (F316/F316L): order code for "Process connection", option D5S

Alloy C22: order code for "Process connection", option D5C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
100	220	180	8 × Ø18	20	107.1	1 127/1 400 ¹⁾
150	285	240	8 × Ø22	22	159.3	1330/1700 ¹⁾
250	405	355	12 × Ø26	26	260.4	1775

Surface roughness (flange): EN 1092-1 Form B1 (DIN 2526 Form C), Ra 3.2 to 12.5 μm

1) Installed length in accordance with NAMUR recommendation NE 132 optionally available (order code for "Process connection", option D1N or D5N (with groove))

Flange similar to EN 1092-1 (DIN 2501): PN16 with reduction in nominal diameter 1.4404 (F316/F316L									
DN [mm]	Reduction to DN [mm]	Order code "Process connection", Option	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]	
100	80	DHS	220	180	8 × Ø18	20	107.1	874	
150	100	DJS	285	240	8 × Ø22	22	159.3	1167	
200 150 DLS 340 295 12 × Ø22 24 206.5 1461									
Surface ro	oughness (flang	e): EN 1092-1 Form	B1 (DIN 2	526 Form	C), Ra 3.2 to 12	.5 µm			

Flange similar to EN 1092-1 (DIN 2501): PN 40

1.4404 (F316/F316L): order code for "Process connection", option D2S

Alloy C22: order code for "Process connection", option D2C

Flange with groove similar to EN 1092-1 Form D (DIN 2512N): PN 40

1.4404 (F316/F316L): order code for "Process connection", option D6S

Alloy C22: order code for "Process connection", option D6C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 ¹⁾	95	65	4 × Ø14	16	17.3	370/510 ²⁾
15	95	65	4 × Ø14	16	17.3	404/510 ²⁾
25	115	85	4 × Ø14	18	28.5	440/600 ²⁾
40	150	110	4 × Ø18	18	43.1	550
50	165	125	4 × Ø18	20	54.5	715/715 ²⁾
80	200	160	8 × Ø18	24	82.5	840/915 ²⁾
100	235	190	8 × Ø22	24	107.1	1 127
150	300	250	8 × Ø26	28	159.3	1370
250	450	385	12 × Ø33	38	258.8	1845

1) DN 8 with DN 15 flanges as standard

2) Installed length in accordance with NAMUR recommendation NE 132 optionally available (order code for "Process connection", option D2N or D6N (with groove))

Surface roughness (flange): EN 1092-1 Form B1 (DIN 2526 Form C), Ra 3.2 to 12.5 μm

Flange similar to EN 1092-1 (DIN 2501): PN 40 (with DN 25 flanges) 1.4404 (F316/F316L): order code for "Process connection", option R2S									
DN A B C D E L [mm] [mm] [mm] [mm] [mm]									
8	115	85	4 × Ø14	18	28.5	440			
15 115 85 4 × Ø14 18 28.5 440									
Surface roughn	ness (flange): EN	1092-1 Form F	31 (DIN 2526 Form	C), Ra 3.2 to 12	2.5 µm				

	Flange similar to EN 1092-1 (DIN 2501): PN 40 with reduction in nominal diameter 1.4404 (F316/F316L)										
DN [mm]	Reduction to DN [mm]	Order code "Process connection", Option	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
50	40	DFS	165	125	4 × Ø18	20	54.5	555			
80	50	DGS	200	160	8 × Ø18	24	82.5	840			
100	80	DIS	235	190	8 × Ø22	24	107.1	874			
150	150 100 DKS 300 250 8 × Ø26 28 159.3 1167										
200 150 DMS 375 320 12 × Ø30 34 206.5 1461											
Surface re	oughness (flang	e): EN 1092-1 Form	B1 (DIN 2	526 Form	C), Ra 3.2 to 12	.5 µm					

Flange similar to EN 1092-1 (DIN 2501): PN 63

1.4404 (F316/F316L): order code for "Process connection", option D3S

Alloy C22: order code for "Process connection", option D3C

Flange with groove similar to EN 1092-1 Form D (DIN 2512N): PN 63

1.4404 (F316/F316L): order code for "Process connection", option D7S

Alloy C22: order code for "Process connection", option D7C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
50	180	135	4 × Ø22	26	54.5	724
80	215	170	8 × Ø22	28	81.7	875
100	250	200	8 × Ø26	30	106.3	1127
150	345	280	8 × Ø33	36	157.1	1410
250	470	400	12 × Ø36	46	255.4	1885

Surface roughness (flange):

EN 1092-1 Form B1 (DIN 2526 Form C), Ra 3.2 to 12.5 μm EN 1092-1 Form B2 (DIN 2526 Form E), Ra 0.8 to 3.2 μm

Flange similar to EN 1092-1 (DIN 2501): PN 100

1.4404 (F316/F316L): order code for "Process connection", option D4S

Alloy C22: order code for "Process connection", option D4C

Flange with groove similar to EN 1092-1 Form D (DIN 2512N): PN 100 $\,$

1.4404 (F316/F316L): order code for "Process connection", option D8S

Alloy C22: order code for "Process connection", option D8C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 ¹⁾	105	75	4 × Ø14	20	17.3	400
15	105	75	4 × Ø14	20	17.3	420
25	140	100	4 × Ø18	24	28.5	470
40	170	125	4 × Ø22	26	42.5	590
50	195	145	4 × Ø26	28	53.9	740
80	230	180	8 × Ø26	32	80.9	885
100	265	210	8 × Ø30	36	104.3	1127
150	355	290	12 × Ø33	44	154.0	1450
	(6)			=\ = 00.		

Surface roughness (flange): EN 1092-1 Form B2 (DIN 2526 Form E), Ra 0.8 to 3.2 μm

1) DN 8 with DN 15 flanges as standard

Flange similar to EN 1092-1 (DIN 2501): PN 100 $\,$

Alloy C22: order code for "Process connection", option ${\bf D4C}$

Flange with groove similar to EN 1092-1 Form D (DIN 2512N): PN 100

Alloy C22: order code for "Process connection", option D8C

DN	A	B	C	D	E	L
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
250	505	430	12 × Ø39	60	248.0	1949

Surface roughness (flange): EN 1092-1 Form B2 (DIN 2526 Form E), Ra 0.8 to 3.2 μm

76

1.4404 (F316	Flange similar to ASME B16.5: Class 150 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
8 ¹⁾	90	60.3	4 × Ø15.7	11.2	15.7	370					
15	90	60.3	4 × Ø15.7	11.2	15.7	404					
25	110	79.4	4 × Ø15.7	14.2	26.7	440					
40	125	98.4	4 × Ø15.9	15.9	40.9	550					
50	150	120.7	4 × Ø19.1	19.1	52.6	715					
80	190	152.4	4 × Ø19.1	23.9	78.0	840					
100	230	190.5	8 × Ø19.1	23.9	102.4	1127					
150	280	241.3	8 × Ø22.4	25.4	154.2	1398					
250	405	362	12 × Ø25.4	30.2	254.5	1832					
Surface rough	Surface roughness (flange): Ra 3.2 to 6.3 µm										

	Flange similar to ASME B16.5: Class 150 with reduction in nominal diameter 1.4404 (F316/F316L)										
DN [mm]	Reduction to DN [mm]	Order code "Process connection", Option	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
50	40	AHS	150	120.7	4 × Ø19.1	19.1	52.6	550			
80	50	AJS	190	152.4	4 × Ø19.1	23.9	78.0	720			
100	80	ALS	230	190.5	8 × Ø19.1	23.9	102.4	874			
150	150 100 ANS 280 241.3 8 × Ø22.4 25.4 154.2 1167										
200 150 APS 345 298.5 8 × Ø22.4 29 202.7 1461											
Surface ro	oughness (flang	e): Ra 3.2 to 6.3 µm					1				

1.4404 (F316	Flange similar to ASME B16.5: Class 300 1.4404 (F316/F316L): order code for "Process connection", option ABS Alloy C22: order code for "Process connection", option ABC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
8 ¹⁾	95	66.7	4 × Ø15.7	14.2	15.7	370					
15	95	66.7	4 × Ø15.7	14.2	15.7	404					
25	125	88.9	4 × Ø19.1	17.5	26.7	440					
40	155	114.3	4 × Ø22.3	20.6	40.9	550					
50	165	127	8 × Ø19.1	22.3	52.6	715					
80	210	168.3	8 × Ø22.3	28.4	78.0	840					
100	255	200	8 × Ø22.3	31.7	102.4	1127					
150	320	269.9	12 × Ø22.3	36.5	154.2	1417					
250 445 387.4 16 × Ø28.4 47.4 254.5 1863											
Surface rough	ness (flange): F	Ra 3.2 to 6.3 µn	1								

1) DN 8 with DN 15 flanges as standard

	Flange similar to ASME B16.5: Class 300 with reduction in nominal diameter 1.4404 (F316/F316L)												
DN [mm]	Reduction to DN [mm]	Order code "Process connection", Option	ocess [mm] [mm] [mm] [mm] [mm]		E [mm]	L [mm]							
50	40	AIS	165	127	8 × Ø19.1	22.3	52.6	615					
80	50	AKS	210	168.3	8 × Ø22.3	28.4	78.0	732					
100	80	AMS	255	200	8 × Ø22.3	31.7	102.4	894					
150	100	AOS	320	269.9	12 × Ø22.3	36.5	154.2	1187					
200	200 150 AQS 380 330.2 12 × Ø25.4 41.7 202.7 1461												
Surface ro	oughness (flang	e): Ra 3.2 to 6.3 μm											

1.4404 (F316	Flange similar to ASME B16.5: Class 600 1.4404 (F316/F316L): order code for "Process connection", option ACS Alloy C22: order code for "Process connection", option ACC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]						
8 ¹⁾	95	66.7	4 × Ø15.7	20.6	13.9	400						
15	95	66.7	4 × Ø15.7	20.6	13.9	420						
25	125	88.9	4 × Ø19.1	23.9	24.3	490						
40	155	114.3	4 × Ø22.3	28.7	38.1	600						
50	165	127	8 × Ø19.1	31.8	49.2	742						
80	210	168.3	8 × Ø22.3	38.2	73.7	900						
100	275	215.9	8 × Ø25.4	48.4	97.3	1157						
150	355	292.1	12 × Ø28.4	47.8	154.2	1467						
250	250 510 431.8 16 × Ø35.1 69.9 254.5 1946											
Surface rough	ness (flange): F	la 3.2 to 6.3 µn	n	1	1	1						

Flange JIS B2220: 10K 1.4404 (F316/F316L): order code for "Process connection", option NDS Alloy C22: order code for "Process connection", option NDC											
DN A B C D E L [mm] [mm] [mm] [mm] [mm]											
50	155	120	4 × Ø19	16	50	715					
80	185	150	8 × Ø19	18	80	832					
100	210	175	8 × Ø19	18	100	1127					
150	280	240	8 × Ø23	22	150	1354					
250 400 355 12 × Ø25 24 250 1775											
Surface roughr	ness (flange): Ra	a 3.2 to 6.3 µm									

1.4404 (F316	Flange JIS B2220: 20K 1.4404 (F316/F316L): order code for "Process connection", option NES Alloy C22: order code for "Process connection", option NEC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]						
8 1)	95	70	4 × Ø15	14	15	370						
15	95	70	4 × Ø15	14	15	404						
25	125	90	4 × Ø19	16	25	440						
40	140	105	4 × Ø19	18	40	550						
50	155	120	8 × Ø19	18	50	715						
80	200	160	8 × Ø23	22	80	832						
100	225	185	8 × Ø23	24	100	1127						
150	305	260	12 × Ø25	28	150	1386						
250	250 430 380 12 × Ø27 34 250 1845											
Surface roughi	ness (flange): Ra	a 1.6 to 3.2 µm										


1.4404 (F316	Flange JIS B2220: 40K 1.4404 (F316/F316L): order code for "Process connection", option NGS Alloy C22: order code for "Process connection", option NGC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]						
8 1)	115	80	4 × Ø19	20	15	400						
15	115	80	4 × Ø19	20	15	425						
25	130	95	4 × Ø19	22	25	485						
40	160	120	4 × Ø23	24	38	600						
50	165	130	8 × Ø19	26	50	760						
80	210	170	8 × Ø23	32	75	890						
100	250	205	8 × Ø25	36	100	1167						
150	150 355 295 12 × Ø33 44 150 1498											
Surface rough	ness (flange): Ra	a 1.6 to 3.2 µm										

1) DN 8 with DN 15 flanges as standard

1.4404 (F316	Flange JIS B2220: 63K 1.4404 (F316/F316L): order code for "Process connection", option NHS Alloy C22: order code for "Process connection", option NHC												
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]							
8 ¹⁾	120	85	4 × Ø19	23	12	420							
15	120	85	4 × Ø19	23	12	440							
25	140	100	4 × Ø23	27	22	494							
40	175	130	4 × Ø25	32	35	620							
50	185	145	8 × Ø23	34	48	775							
80	230	185	8 × Ø25	40	73	915							
100	270	220	8 × Ø27	44	98	1167							

Flange JIS B2220: 63K 1.4404 (F316/F316L): order code for "Process connection", option NHS Alloy C22: order code for "Process connection", option NHC										
DN A B C D E L [mm] [mm] [mm] [mm] [mm]										
150 365 305 12 × Ø33 54 146 1528										
Surface roughi	ness (flange): Ra	a 1 6 to 3 2 um								

Fixed flange DIN 11864-2



 \blacksquare 39 Detail X: Asymmetrical process connection; the part shown in blue is provided by the supplier.

Length tolerance for dimension L in mm: +1.5 / -2.0

Flange DIN11864-2 Form A, for pipe according to DIN11866 series A, flange with notch 1.4404 (316/316L) Order code for "Process connection", option KCS

- 1	-		, ,				
	DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
	8 1)	54	37	4 × Ø9	10	10	387
	15	59	42	4 × Ø9	10	16	418
	25	70	53	4 × Ø9	10	26	454
	40	82	65	4 × Ø9	10	38	560
	50	94	77	4 × Ø9	10	50	720
	80	133	112	8 × Ø11	12	81	900
	100	159	137	8 × Ø11	14	100	1 127

3A version available: order code for "Additional approval", option LP in conjunction with


Ra $\leq 0.76~\mu m$: order code for "Measuring tube material", option SB, SE, SJ, SL or

 $Ra \le 0.38 \ \mu m$: order code for "Measuring tube material", option SC, SF, SK, SM

 $Ra \le 0.38 \ \mu m$ electropolished: order code for "Measuring tube material", option BC, BG

1) DN 8 with DN 10 flanges as standard

Lap joint flange EN 1092-1, ASME B16.5, JIS B2220



Length tolerance for dimension L in mm: +1.5 / -2.0

1.4301 (F	Lap joint flange similar to EN 1092-1 Form D: PN 40 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option DAC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L _{diff} 1) [mm]				
8 ²⁾	95	65	4 × Ø14	14.5	45	17.3	370	0				
15	95	65	4 × Ø14	14.5	45	17.3	404	0				
25	115	85	4 × Ø14	16.5	68	28.5	444	+4				
40	150	110	4 × Ø18	21	88	43.1	560	+10				
50	165	125	4 × Ø18	23	102	54.5	719	+4				
80	200	160	8 × Ø18	29	138	82.5	848	+8				
100	100 235 190 8 × Ø22 34 162 107.1 1131 +4											
Surface rou	ighness (fla	nge): Ra 3.2	to 12.5 µm									

- 1) Difference to installed length of the welding neck flange (order code for "Process connection", option D2C)
- 2) DN 8 with DN 15 flanges as standard

1.4301 (F	Lap joint flange similar to ASME B16.5: Class 150 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option ADC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L _{diff} 1) [mm]				
8 ²⁾	90	60.3	4 × Ø 15.7	15	35.1	15.7	370	0				
15	90	60.3	4 × Ø 15.7	15	35.1	15.7	404	0				
25	110	79.4	4 × Ø 15.7	16	50.8	26.7	440	0				
40	125	98.4	4 × Ø 15.7	15.9	73.2	40.9	550	0				
50	150	120.7	4 × Ø 19.1	19	91.9	52.6	715	0				
80	190	152.4	4 × Ø 19.1	22.3	127.0	78.0	840	0				
100	100 230 190.5 8 × Ø 19.1 26 157.2 102.4 1127 0											
Surface rou	ighness (fla	nge): Ra 3.2	to 12.5 µm									

- 1) Difference to installed length of the welding neck flange (order code for "Process connection", option AAC)
- 2) DN 8 with DN 15 flanges as standard

1.4301 (F	Lap joint flange similar to ASME B16.5: Class 300 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option AEC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L _{diff} 1) [mm]				
8 ²⁾	95	66.7	4 × Ø 15.7	16.5	35.1	15.7	376	+6				
15	95	66.7	4 × Ø 15.7	16.5	35.1	15.7	406	+2				
25	125	88.9	4 × Ø 19.1	21.0	50.8	26.7	450	+10				
40	155	114.3	4 × Ø 22.3	23.0	73.2	40.9	564	+14				
50	165	127	8 × Ø 19.1	25.5	91.9	52.6	717	+2				
80	210	168.3	8 × Ø 22.3	31.0	127.0	78.0	852.6	+12.6				
100 255 200 8 × Ø 22.3 32.0 157.2 102.4 1139 +12												
Surface rou	ıghness (fla	nge): Ra 3.2	to 12.5 µm									

- Difference to installed length of the welding neck flange (order code for "Process connection", option ABC)
- 2) DN 8 with DN 15 flanges as standard

1.4301 (F	Lap joint flange similar to ASME B16.5: Class 600 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option AFC												
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L _{diff} 1) [mm]					
8 ²⁾	95	66.7	4 × Ø 15.7	17.0	35.1	13.9	400	0					
15	95	66.7	4 × Ø 15.7	17.0	35.1	13.9	420	0					
25	125	88.9	4 × Ø 19.1	21.5	50.8	24.3	490	0					
40	155	114.3	4 × Ø 22.3	25.0	73.2	38.1	600	0					
50	165	127	8 × Ø 19.1	28.0	91.9	49.2	742	0					
80	210	168.3	8 × Ø 22.3	35.0	127.0	73.7	900	0					
100 275 215.9 8 × Ø 25.4 44.0 157.2 97.3 1167 +10													
Surface rou	ighness (fla	nge): Ra 3.2	to 12.5 µm										


- 1) Difference to installed length of the welding neck flange (order code for "Process connection", option ACC)
- DN 8 with DN 15 flanges as standard 2)

1.4301 (F3	Lap joint flange JIS B2220: 20K 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option NIC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L _{diff} 1) [mm]				
8 ²⁾	95	70	4 × Ø 15	14	51	15	370	0				
15	95	70	4 × Ø 15	14	51	15	404	0				
25	125	90	4 × Ø 19	18.5	67	25	440	0				
40	140	105	4 × Ø 19	18.5	81	40	550	0				
50	155	120	8 × Ø 19	23	96	50	715	0				
80	200	160	8 × Ø 23	29	132	80	844	+12				
100	225	185	8 × Ø 23	29	160	100	1127	0				
Surface rou	ghness (flan	ge): Ra 3.2 to	ο 12.5 μm									

- Difference to installed length of the welding neck flange (order code for "Process connection", option NEC) DN 8 with DN 15 flanges as standard $\,$ 1)
- 2)

Clamp connections

Tri-Clamp



Length tolerance for dimension L in mm: +1.5 / -2.0

Tri-Clamp (1/2"), for pipe according to DIN 11866 series C 1.4404 (316/316L) Order code for "Process connection", option FDW DN В Clamp Α [mm] [in] [mm] [mm] [mm] 8 25.0 9.5 367 15 1/2 25.0 9.5 398

3-A version available: order code for "Additional approval", option LP in conjunction with

 $Ra \leq 0.76~\mu m$: order code for "Measuring tube material", option SB, SE, SJ, SL or

 $Ra \le 0.38 \ \mu m$: order code for "Measuring tube material", option SC, SF, SK, SM

 $Ra \le 0.38 \ \mu m$ electropolished: order code for "Measuring tube material", option BC, BG

Tri-Clamp (≥ 1"), for pipe according to DIN 11866 series C 1.4404 (316/316L) Order code for "Process connection", option FTS										
DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]						
8	1	50.4	22.1	367						
15	1	50.4	22.1	398						
25	1	50.4	22.1	434						
40	11/2	50.4	34.8	560						
50	2	63.9	47.5	720						
80	3	90.9	72.9	900						
100	4	118.9	97.4	1 127						

3-A version available: order code for "Additional approval", option LP in conjunction with


 $Ra \leq 0.76~\mu m$: order code for "Measuring tube material", option SB, SE, SJ, SL or

 $Ra \le 0.38 \ \mu m$: order code for "Measuring tube material", option SC, SF, SK, SM

Ra $\leq 0.38 \, \mu m$ electropolished: order code for "Measuring tube material", option BC, BG

Threaded couplings

Threaded adapter DIN 11851, DIN11864-1, SMS 1145



Length tolerance for dimension L in mm: +1.5 / -2.0

Threaded adapter DIN 11851, for pipe according to DIN11866 series A 1.4404 (316/316L) Order code for "Process connection", option FMW									
DN [mm]	A [in]	B [mm]	L [mm]						
8	Rd 34 × ½	16	367						
15	Rd 34 × ½	16	398						
25	Rd 52 × 1/ ₆	26	434						
40	Rd 65 × ½	38	560						
50	Rd 78 × ½	50	720						
80	Rd 110 × 1/4	81	900						
100	Rd 130 × 1/4	100	1127						
3-A version available: ord	der code for "Additional approval",	option LP in conjunction wi	th						

Ra \leq 0.76 μ m: order code for "Measuring tube material", option SB, SE, SJ, SL

Threaded adapter DIN11864-1 Form A, for pipe according to DIN11866 series A 1.4404 (316/316L) Order code for "Process connection", option FLW									
DN A B L [mm] [mm]									
8	Rd 28 × 1/ ₈	10	367						
15	Rd 34 × 1/8	16	398						
25	Rd 52 × 1/ ₈	26	434						
40	Rd 65 × ½	38	560						
50	Rd 78 × 1/ ₆	50	720						
80	Rd 110 × 1/4	81	900						
100	Rd 130 × ¹ / ₄	100	1127						

3-A version available: order code for "Additional approval", option LP in conjunction with

 $Ra \le 0.76 \ \mu m$: order code for "Measuring tube material", option SB, SE, SJ, SL or

 $Ra \leq 0.38~\mu m$: order code for "Measuring tube material", option SC, SF, SK, SM

 $Ra \le 0.38 \ \mu m$ electropolished: order code for "Measuring tube material", option BC, BG


Threaded adapter SMS 1145 1.4404 (316/316L)

Order code for "Process connection", option SCS

	/ - r		
DN [mm]	A [in]	B [mm]	L [mm]
8	Rd 40 × 1/ ₆	22.6	367
15	Rd 40 × 1/ ₆	22.6	398
25	Rd 40 × 1/ ₆	22.6	434
40	Rd 60 × 1/ ₆	35.6	560
50	Rd 70 × 1/ ₆	48.6	720
80	Rd 98 × 1/ ₆	72.9	900
100	Rd 132 × ½	97.6	1127

³⁻A version available: order code for "Additional approval", option LP in conjunction with Ra $\leq 0.76~\mu m$: order code for "Measuring tube material", option SB, SE, SJ, SL

Threaded adapter ISO 2853



Length tolerance for dimension L in mm: +1.5 / -2.0

Threaded adapter ISO 2853, for pipe according to ISO 2037 1.4404 (316/316L) Order code for "Process connection", option JSF										
DN A ¹⁾ B L [mm] [mm]										
8	37.13	22.6	367							
15	37.13	22.6	398							
25	37.13	22.6	434							
40	52.68	35.6	560							
50	64.16	48.6	720							
80	91.19	72.9	900							
100	118.21	97.6	1127							


3-A version available: order code for "Additional approval", option LP in conjunction with

Ra $\leq 0.76~\mu m$: order code for "Measuring tube material", option SB, SE, SJ, SL or Ra $\leq 0.38~\mu m$: order code for "Measuring tube material", option SC, SF, SK, SM

 $Ra \le 0.38 \ \mu m$ electropolished: order code for "Measuring tube material", option BC, BG

Max. thread diameter according to ISO 2853 Annex A 1)

VCO



Length tolerance for dimension L in mm: +1.5 / -2.0


8-VCO-4 (½") 1.4404 (316/316L) Order code for "Process conne	, f								
DN [mm]	A [in]	B [mm]	L [mm]						
8	AF 1	10.2	390						

12-VCO-4 (¾") 1.4404 (316/316L) Order code for "Process conr	nection", option CWS		
DN [mm]	A [in]	B [mm]	L [mm]
15	AF 1½	15.7	430

88

Accessories

Rupture disk/purge connections




€ 40

- Connection nipple for purge connections: order code for "Sensor options", option CH "Purge connection"
- Connection nipple with rupture disk: order code for "Sensor option", option CA "Rupture disk"


DN	A	L
[mm]	[mm]	[mm]
8	62	216
15	62	220
25	62	260
40	67	310
50	79	452
80	101	560
100	120	684
150	141	880
250	182	380

Weather protection cover



■ 41 Engineering unit mm (in)

Remote display and operating module DKX001




■ 42 Engineering unit mm (in)

External WLAN antenna

The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



■ 43 Engineering unit mm (in)

External WLAN antenna mounted with cable


The external WLAN antenna can be mounted separately from the transmitter if the transmission/reception conditions at the transmitter mounting location are poor.



■ 44 Engineering unit mm (in)

Dimensions in US units

Compact version



A003378

Order code for "Housing", option A "Aluminum, coated"

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F ²⁾³⁾	G ⁴⁾	Н	I 4)	К	L	М
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3/8	6.65	2.68	3.98	2.95	10.22	13.17	7.87	2.32	5.55	0.21	5)	2.76
1/2	6.65	2.68	3.98	2.95	10.22	13.17	7.87	2.32	5.55	0.33	5)	2.76
1	6.65	2.68	3.98	2.95 ⁶⁾	10.22	13.17	7.87	2.32	5.55	0.47	5)	2.76
1½	6.65	2.68	3.98	4.13	10.41	14.55	7.87	2.32	5.55	0.69	5)	3.11
2	6.65	2.68	3.98	5.55	10.81	16.36	7.87	2.32	5.55	1.02	5)	3.90
3	6.65	2.68	3.98	7.87	11.59	19.47	7.87	2.32	5.55	1.59	5)	5.47
4	6.65	2.68	3.98	10.00	12.30	22.30	7.87	2.32	5.55	2.02	5)	6.93
6	6.65	2.68	3.98	14.88	13.13	28.01	7.87	2.32	5.55	2.71	5)	8.58
10	6.65	2.68	3.98	21.57	14.86	36.44	7.87	2.32	5.55	4.03	5)	12.01

- 1) Depending on the cable gland used: values up to + 1.18 in
- 2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +2.76 in
- 3) With order code for "Measuring tube material", option TS, TT, TU: values +4.02 in
- 4) For version without local display: values 1.18 in
- 5) Depending on the process connection
- 6) With order code for "Measuring tube material", option TT, TU: value +0.98 in

Order code for "Housing", option A "Aluminum, coated"; Ex d

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G ⁴⁾	Н	I	K	L	M
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3/8	7.40	3.35	4.06	2.95	10.26	13.21	8.54	2.28	6.26	0.21	5)	2.76
1/2	7.40	3.35	4.06	2.95	10.26	13.21	8.54	2.28	6.26	0.33	5)	2.76
1	7.40	3.35	4.06	2.95 ⁶⁾	10.26	13.21	8.54	2.28	6.26	0.47	5)	2.76
1½	7.40	3.35	4.06	4.13	10.43	14.57	8.54	2.28	6.26	0.69	5)	3.11
2	7.40	3.35	4.06	5.55	10.83	16.38	8.54	2.28	6.26	1.02	5)	3.90
3	7.40	3.35	4.06	7.87	11.61	19.49	8.54	2.28	6.26	1.59	5)	5.47
4	7.40	3.35	4.06	10	12.34	22.34	8.54	2.28	6.26	2.02	5)	6.93

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G 4)	Н	I	K	L	M
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
6	7.40	3.35	4.06	14.88	13.17	28.05	8.54	2.28	6.26	2.71	5)	8.58
10	7.40	3.35	4.06	21.57	14.88	36.46	8.54	2.28	6.26	4.03	5)	12.01

- 1) Depending on the cable gland used: values up to \pm 1.18 in
- 2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +2.76 in
- 3) With order code for "Measuring tube material", option TS, TT, TU: values +4.02 in
- 4) For version without local display: values 1.57 in
- 5) Depending on the process connection
- 6) With order code for "Measuring tube material", option TT, TU: value +0.98 in

Order code for "Housing", option B "Stainless, hygienic"

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G ⁴⁾	Н	I	K	L	М
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3/8	7.20	2.87	4.33	2.95	10.22	13.17	7.87	2.56	5.31	0.21	5)	2.76
1/2	7.20	2.87	4.33	2.95	10.22	13.17	7.87	2.56	5.31	0.33	5)	2.76
1	7.20	2.87	4.33	2.95 ⁶⁾	10.22	13.17	7.87	2.56	5.31	0.47	5)	2.76
11/2	7.20	2.87	4.33	4.13	10.41	14.55	7.87	2.56	5.31	0.69	5)	3.11
2	7.20	2.87	4.33	5.55	10.81	16.36	7.87	2.56	5.31	1.02	5)	3.90
3	7.20	2.87	4.33	7.87	11.59	19.47	7.87	2.56	5.31	1.59	5)	5.47
4	7.20	2.87	4.33	10.00	12.30	22.30	7.87	2.56	5.31	2.02	5)	6.93
6	7.20	2.87	4.33	14.88	13.13	28.01	7.87	2.56	5.31	2.71	5)	8.58
10	7.20	2.87	4.33	21.57	14.86	36.44	7.87	2.56	5.31	4.03	5)	12.01

- 1) Depending on the cable gland used: values up to + 1.18 in
- With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +2.76 in
- 3) With order code for "Measuring tube material", option TS, TT, TU: values +4.02 in
- 4) For version without local display: values 0.51 in
- 5) Depending on the process connection
- 6) With order code for "Measuring tube material", option TT, TU: value +0.98 in

Order code for "Housing", option L "Cast, stainless"


DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G	Н	I	K	L	M
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3/8	7.32	3.35	3.98	2.95	10.24	13.19	8.54	2.36	6.18	0.21	4)	2.76
1/2	7.32	3.35	3.98	2.95	10.24	13.19	8.54	2.36	6.18	0.33	4)	2.76
1	7.32	3.35	3.98	2.95 ⁵⁾	10.24	13.19	8.54	2.36	6.18	0.47	4)	2.76
1½	7.32	3.35	3.98	4.13	10.41	14.55	8.54	2.36	6.18	0.69	4)	3.11
2	7.32	3.35	3.98	5.55	10.81	16.36	8.54	2.36	6.18	1.02	4)	3.90
3	7.32	3.35	3.98	7.87	11.59	19.47	8.54	2.36	6.18	1.59	4)	5.47
4	7.32	3.35	3.98	10	12.32	22.32	8.54	2.36	6.18	2.02	4)	6.93

DN	A 1)	B 1)	С	D	E ²⁾³⁾	F	G	Н	I	K	L	M
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
6	7.32	3.35	3.98	14.88	13.15	28.03	8.54	2.36	6.18	2.71	4)	8.58
10	7.32	3.35	3.98	21.57	14.86	36.44	8.54	2.36	6.18	4.03	4)	12.01

- 1) Depending on the cable gland used: values up to \pm 1.18 in
- 2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH, LA: values +2.76 in
- 3) With order code for "Measuring tube material", option TS, TT, TU: values +4.02 in
- 4) Depending on the process connection
- 5) With order code for "Measuring tube material", option TT, TU: value +0.98 in

Flange connections

Fixed flange ASME B16.5



Length tolerance for dimension L in inches: • DN \leq 4": +0.06/-0.08 • DN \geq 6": \pm 0.14

1.4404 (F31	Flange similar to ASME B16.5: Class 150 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC										
DN [in]	[in] [in] [in] [in] [in]										
3/8 1)	3.54	2.37	4 × Ø0.62	0.44	0.62	14.57					
1/2	½ 3.54 2.37 4 × Ø0.62 0.44 0.62 15.91										
1	4.33	3.13	4 × Ø0.62	0.56	1.05	17.32					
11/2	4.92	3.87	4 × Ø0.63	0.63	1.61	21.65					
2	5.91	4.75	4 × Ø0.75	0.75	2.07	28.15					
3	7.48	6.00	4 × Ø0.75	0.94	3.07	33.07					
4	9.06	7.50	8 × Ø0.75	0.94	4.03	44.37					
6 11.02 9.50 8 × Ø0.88 1 6.07 55.04											
10 15.94 14.25 12 × Ø1.0 1.19 10.02 72.13											
Surface roughness (flange): Ra 126 to 248 µin											

DN $^3\!/\!_8$ with DN $^1\!/\!_2$ flanges as standard 1)

	Flange similar to ASME B16.5: Class 150 with reduction in nominal diameter 1.4404 (F316/F316L)									
DN [in]	Reduction to DN [in]	Order code "Process connection", Option	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]		
2	1½	AHS	5.91	4.75	4 × Ø0.75	0.75	2.07	21.65		
3	2	AJS	7.48	6	4 × Ø0.75	0.94	3.07	28.35		
4	3	ALS	9.06	7.5	8 × Ø0.75	0.94	4.03	34.41		
6	6 4 ANS 11.02 9.5 8 × Ø0.88 1 6.07 45.94									
8 6 APS 13.58 11.75 8 × Ø0.88 1.14 7.98 57.52										
Surface roughness (flange): Ra 126 to 248 µin										

1.4404 (F3	Flange similar to ASME B16.5: Class 300 1.4404 (F316/F316L): order code for "Process connection", option ABS Alloy C22: order code for "Process connection", option ABC									
DN [in]	[in] [in] [in] [in] [in]									
3/8 1)	3.74	2.63	4 × Ø0.62	0.56	0.62	14.57				
1/2	3.74	2.63	4 × Ø0.62	0.56	0.62	15.91				
1	4.92	3.50	4 × Ø0.75	0.69	1.05	17.32				
11/2	6.10	4.50	4 × Ø0.88	0.81	1.61	21.65				
2	6.50	5.00	8 × Ø0.75	0.88	2.07	28.15				
3	8.27	6.63	8 × Ø0.88	1.12	3.07	33.07				
4	10.04	7.87	8 × Ø0.88	1.25	4.03	44.37				
6 12.6 10.63 12 × Ø0.88 1.44 6.07 55.79										
10 17.52 15.25 16 × Ø1.12 1.87 10.02 73.35										
Surface roughness (flange): Ra 126 to 248 µin										


1) DN $\frac{3}{8}$ " with DN $\frac{1}{2}$ " flanges as standard

	Flange similar to ASME B16.5: Class 300 with reduction in nominal diameter 1.4404 (F316/F316L)										
DN [in]	Reduction to DN [in]	Order code "Process connection", Option	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]			
2	1½	AIS	6.5	5	8 × Ø0.75	0.88	2.07	24.21			
3	2	AKS	8.27	6.63	8 × Ø0.88	1.12	3.07	28.82			
4	3	AMS	10.04	7.87	8 × Ø0.88	1.25	4.03	35.2			
6	6 4 AOS 12.6 10.63 12 × Ø0.88 1.44 6.07 46.73										
8 6 AQS 14.96 13 12 × Ø1 1.64 7.98 57.52											
Surface roughness (flange): Ra 126 to 248 μin											

1.4404 (F3	Flange similar to ASME B16.5: Class 600 1.4404 (F316/F316L): order code for "Process connection", option ACS Alloy C22: order code for "Process connection", option ACC									
DN [in]										
³ / ₈ ¹⁾ 3.74 2.63 4 × Ø0.62 0.81 0.55 15.75										
1/2	1/2 3.74 2.63 4 × Ø0.62 0.81 0.55 16.54									
1	4.92	3.50	4 × Ø0.75	0.94	0.96	19.29				
1½	6.10	4.50	4 × Ø0.88	1.13	1.5	23.62				
2	6.50	5.00	8 × Ø0.75	1.25	1.94	29.21				
3	8.27	6.63	8 × Ø0.88	1.5	2.9	35.43				
4	10.83	8.50	8 × Ø1.00	1.91	3.83	45.55				
6 13.98 11.50 12 × Ø1.12 1.88 6.07 57.76										
10 20.08 17.00 16 × Ø1.38 2.75 10.02 76.61										
Surface rou	Surface roughness (flange): Ra 126 to 248 µin									

1) DN $^3\!/_8$ with DN $^1\!/_2$ flanges as standard

Lap joint flange ASME B16.5



Length tolerance for dimension L in inch: +0.06 / -0.08

1.4301 (F	Lap joint flange similar to ASME B16.5: Class 150 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option ADC									
DN [in]	uni									
3/8 2)	3.54	2.37	4 × Ø 0.62	0.59	1.38	0.62	14.57	0		
1/2	3.54	2.37	4 × Ø 0.62	0.59	1.38	0.62	15.91	0		
1	4.33	3.13	4 × Ø 0.62	0.63	2	1.05	17.32	0		
11/2	4.92	3.87	4 × Ø 0.62	0.63	2.88	1.61	21.65	0		
2	5.91	4.75	4 × Ø 0.75	0.75	3.62	2.07	28.15	0		
3 7.48 6.00 4 × Ø 0.75 0.88 5 3.07 33.07 0										
4 9.06 7.50 8 × Ø 0.75 1.02 6.19 4.03 44.37 0										
Surface rou	Surface roughness (flange): Ra 126 to 492 µin									

- 1) Difference to installed length of the welding neck flange (order code for "Process connection", option AAC)
- 2) DN $\frac{3}{8}$ " with DN $\frac{1}{2}$ " flanges as standard

1.4301 (F	Lap joint flange similar to ASME B16.5: Class 300 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option AEC									
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]	L _{diff} 1) [in]		
3/8 2)	3.74	2.63	4 × Ø 0.62	0.65	1.38	0.62	14.8	+0.23		
1/2	3.74	2.63	4 × Ø 0.62	0.65	1.38	0.62	15.98	+0.07		
1	4.92	3.50	4 × Ø 0.75	0.83	2	1.05	17.72	+0.40		
1½	6.10	4.50	4 × Ø 0.88	0.91	2.88	1.61	22.2	+0.55		
2	6.50	5.00	8 × Ø 0.75	1	3.62	2.07	28.23	+0.08		
3 8.27 6.63 8 × Ø 0.88 1.22 5 3.07 33.57 +0.50										
4 10.04 7.87 8 × Ø 0.88 1.26 6.19 4.03 44.84 +0.47										
Surface rou	Surface roughness (flange): Ra 126 to 492 µin									

- 1) Difference to installed length of the welding neck flange (order code for "Process connection", option AAC)
- 2) DN $\frac{3}{8}$ " with DN $\frac{1}{2}$ " flanges as standard


1.4301 (F	Lap joint flange similar to ASME B16.5, Class 600 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option AFC									
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]	L _{diff} 1) [in]		
3/8 2)	3.74	2.63	4 × Ø 0.62	0.67	1.38	0.55	15.75	0		
1/2	3.74	2.63	4 × Ø 0.62	0.67	1.38	0.55	16.54	0		
1	4.92	3.50	4 × Ø 0.75	0.85	2	0.96	19.29	0		
1½	6.10	4.50	4 × Ø 0.88	0.98	2.88	1.5	23.62	0		
2	6.50	5.00	8 × Ø 0.75	1.1	3.62	1.94	29.21	0		
3 8.27 6.63 8 × Ø 0.88 1.38 5 2.9 35.43 0										
4 10.83 8.50 8 × Ø 1 1.73 6.19 3.83 45.94 +0.39										
Surface rou	Surface roughness (flange): Ra 126 to 492 µin									

Difference to installed length of the welding neck flange (order code for "Process connection", option AAC) DN $^3/_8$ " with DN $^4/_2$ " flanges as standard

¹⁾ 2)

Clamp connections

Tri-Clamp



Length tolerance for dimension L in inch: +0.06 / -0.08

Tri-Clamp (½"), DIN 11866 series C 1.4404 (316/316L) Order code for "Process connection", option FDW									
DN Clamp A B L [in] [in] [in] [in]									
³ / ₈ ¹ / ₂ 0.98 0.37 14.4									
15.7									

3-A version available: order code for "Additional approval", option LP in conjunction with

 $Ra \le 30~\mu in:$ order code for "Measuring tube material", option SB, SE, SJ, SJ, SL or

 $Ra \le 15 \mu in$: order code for "Measuring tube material", option SC, SF, SK, SM

 $Ra \le 15 \mu in$ electropolished: order code for "Measuring tube material", option BC, BG

Tri-Clamp (≥ 1"), DIN 11866 series C 1.4404 (316/316L) Order code for "Process connection", option FTS				
DN [in]	Clamp [in]	A [in]	B [in]	L [in]
3/8	1	1.98	0.87	14.4
1/2	1	1.98	0.87	15.7
1	1	1.98	0.87	17.1
1½	1½	1.98	1.37	22.0
2	2	2.52	1.87	28.3
3	3	3.58	2.87	35.4
4	4	4.68	3.83	44.4

3-A version available: order code for "Additional approval", option LP in conjunction with


 $Ra \leq 30~\mu in:$ order code for "Measuring tube material", option SB, SE, SJ, SJ, SL or

 $Ra \leq 15~\mu in:$ order code for "Measuring tube material", option SC, SF, SK, SM

 $Ra \le 15$ µin electropolished: order code for "Measuring tube material", option BC, BG

Threaded couplings

Threaded adapter SMS 1145




Length tolerance for dimension L in inch: +0.06 / -0.08

Threaded adapter SMS 1145 1.4404 (316/316L) Order code for "Process connection", option SCS			
DN [in]	A [in]	B [in]	L [in]
3/8	Rd 40 × 1/ ₆	0.89	14.45
1/2	Rd 40 × 1/ ₆	0.89	15.67
1	Rd 40 × 1/ ₆	0.89	17.09
1½	Rd 60 × ½	1.4	22.05
2	Rd 70 × 1/ ₆	1.91	28.35
3	Rd 98 × 1/ ₆	2.87	35.43
4	Rd 132 × 1/ ₆	3.84	44.37

3-A version available: order code for "Additional approval", option LP in conjunction with Ra $\leq 30~\mu in$: order code for "Measuring tube material", option SB, SE, SJ, SL

VCO




Length tolerance for dimension L in inch: +0.06 / -0.08

-	8-VCO-4 (½") 1.4404 (316/316L) Order code for "Process con	nnection", option CVS		
	DN [in]	A [in]	B [in]	L [in]
Г	3/8	AF 1	0.4	15.35

12-VCO-4 (¾") 1.4404 (316/316L) Order code for "Process co			
DN [in]	A [in]	B [in]	L [in]
1/2	AF 1½	0.62	16.93

Accessories


Rupture disk/purge connections



Connection nipple for purge connections: order code for "Sensor options", option CH "Purge connection" Connection nipple with rupture disk: order code for "Sensor option", option CA "Rupture disk"


DN	A	L
[in]	[in]	[in]
3/8	2.44	8.50
1/2	2.44	8.66
1	2.44	10.24
1½	2.64	12.20
2	3.11	17.78
3	3.98	22.0
4	4.72	27.0
6	5.55	34.6
10	7.17	14.96

Weather protection cover



■ 45 Engineering unit mm (in)

Remote display and operating module DKX001




■ 46 Engineering unit mm (in)

External WLAN antenna

The external WLAN antenna is not suitable for use in hygienic applications.


External WLAN antenna mounted on device



■ 47 Engineering unit mm (in)

External WLAN antenna mounted with cable

The external WLAN antenna can be mounted separately from the transmitter if the transmission/reception conditions at the transmitter mounting location are poor.



■ 48 Engineering unit mm (in)

Weight

All values (weight exclusive of packaging material) refer to devices with EN/DIN PN 40 flanges. Weight specifications including transmitter as per order code for "Housing", option A "Aluminum, coated".

Different values due to different transmitter versions:

- Transmitter version for the hazardous area (Order code for "Housing", option A "Aluminum, coated"; Ex d): +2 kg (+4.4 lbs)
- Cast transmitter version, stainless
 (Order code for "Housing", option L "Cast, stainless"): +6 kg (+13 lbs)
- Transmitter version for hygienic area (Order code for "Housing", option B "Stainless, hygienic"): +0.2 kg (+0.44 lbs)

Weight in SI units

DN [mm]	Weight [kg]
8	11
15	12
25	14
40	19
50	30

Endress+Hauser 103

A003359

DN [mm]	Weight [kg]
80	55
100	96
150	154
250	400

Weight in US units

DN [in]	Weight [lbs]
3/8	24
1/2	26
1	31
1½	42
2	66
3	121
4	212
6	340
10	882

Materials

Transmitter housing

Order code for "Housing":

- $\, \bullet \,$ Option A "Aluminum, coated": aluminum, AlSi10Mg, coated
- Option **B** "Stainless, hygienic": stainless steel, 1.4404 (316L)
- Option L "Cast, stainless": cast, stainless steel, 1.4409 (CF3M) similar to 316L

Window material

Order code for "Housing":


- Option **A** "Aluminum, coated": glass
- Option B "Stainless, hygienic": polycarbonate
 Option L "Cast, stainless": glass

Seals

Order code for "Housing":

Option ${\bf B}$ "Stainless, hygienic": EPDM and silicone

Cable entries/cable glands



A002835

■ 49 Possible cable entries/cable glands

- 1 Female thread M20 \times 1.5
- 2 Cable gland $M20 \times 1.5$
- 3 Adapter for cable entry with female thread G ½" or NPT ½"
- 4 Device plug

Order code for "Housing", option A "Aluminum, coated"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material	
Compression fitting M20 × 1.5	Non-Ex: plastic	
Compression many wize ^ 1.5	Z2, D2, Ex d/de: brass with plastic	
Adapter for cable entry with female thread G 1/2"	Nickel-plated brass	
Adapter for cable entry with female thread NPT 1/2"		

Order code for "Housing", option B "Stainless, hygienic"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Plastic
Adapter for cable entry with female thread G 1/2"	Nickel-plated brass
Adapter for cable entry with female thread NPT ½"	

Order code for "Housing", option L "Cast, stainless"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Stainless steel, 1.4404 (316L)
Adapter for cable entry with female thread G ½"	
Adapter for cable entry with female thread NPT ½"	

Device plug

Electrical connection	Material
Plug M12x1	 Socket: Stainless steel, 1.4404 (316L) Contact housing: Polyamide Contacts: Gold-plated brass

Sensor housing

The material of the sensor housing depends on the option selected in the order code for "Measuring tube mat., wetted surface".

Order code for "Measuring tube mat., wetted surface"	Material	
Option HA, SA, SD, TH	Acid and alkali-resistant outer surfaceStainless steel 1.4301 (304)	
	With order code for "Sensor option", option CC "316L Sensor housing": stainless steel, 1.4404 (316L)	
Option SB, SC, SE, SF	Acid and alkali-resistant outer surfaceStainless steel 1.4301 (304)	
Option TS, TT, TU, LA	 Acid and alkali-resistant outer surface Stainless steel, 1.4404 (316L) 	

Measuring tubes

- DN 8 to 100 (3/8 to 4"): stainless steel, 1.4539 (904L); Manifold: stainless steel, 1.4404 (316/316L)
- DN 150 (6"), DN 250 (10"): stainless steel, 1.4404 (316/316L); Manifold: stainless steel, 1.4404 (316/316L)
- DN 8 to 250 (3/8 to 10"): Alloy C22, 2.4602 (UNS N06022); Manifold: Alloy C22, 2.4602 (UNS N06022)

High-temperature version

DN 15 (½"), 25 (1"), 50 to 250 (2 to 10"):

- DN 15 to 100 (½ to 4"): stainless steel, 1.4539 (904L)
- DN 150 (6"), 250 (10"): stainless steel, 1.4404 (316/316L)
- DN 15 to 250 (½ to 10"): Alloy C22, 2.4602 (UNS N06022)

Process connections

- Flanges according to EN 1092-1 (DIN2501) / according to ASME B 16.5 / as per JIS B2220:
 - Stainless steel, 1.4404 (F316/F316L)
 - Alloy C22, 2.4602 (UNS N06022)
 - Lap joint flanges: stainless steel, 1.4301 (F304); wetted parts Alloy C22
- All other process connections: Stainless steel, 1.4404 (316/316L)

High-temperature version

Flanges according to EN 1092-1 (DIN2501) / according to ASME B 16.5 / as per JIS B2220:

- DN 15 to 250 (½ to 10"): stainless steel, 1.4404 (316/316L)
- DN 15 to 250 (½ to 10"): Alloy C22, 2.4602 (UNS N06022)



Available process connections → 107

Seals

Welded process connections without internal seals

Accessories

Protective cover

Stainless steel, 1.4404 (316L)

External WLAN antenna

- Antenna: ASA plastic (acrylonitrile styrene acrylate) and nickel-plated brass
- Adapter: Stainless steel and nickel-plated brass
- Cable: Polyethylene
- Plug: Nickel-plated brass
- Angle bracket: Stainless steel

Process connections

- Fixed flange connections:
 - EN 1092-1 (DIN 2501) flange
 - EN 1092-1 (DIN 2512N) flange
 - NAMUR lengths in accordance with NE 132
 - ASME B16.5 flange
 - JIS B2220 flange
 - DIN 11864-2 Form A flange, DIN 11866 series A, flange with notch
- Clamp connections:

Tri-Clamp (OD tubes), DIN 11866 series C

- Thread:
 - DIN 11851 thread, DIN 11866 series A
 - SMS 1145 thread
 - ISO 2853 thread, ISO 2037
- DIN 11864-1 Form A thread, DIN 11866 series A
- VCO connections:
 - 8-VCO-4
 - 12-VCO-4
- i

Surface roughness

All data refer to parts in contact with the medium.

The following surface roughness categories can be ordered:

Category	Method	Option(s) order code "Measuring tube mat., wetted surface"
Not polished	-	HA. LA, SA, SD, TH, TS, TT, TU
Ra \leq 0.76 µm (30 µin) 1)	Mechanically polished ²⁾	SB, SE
Ra \leq 0.76 µm (30 µin) 1)	Mechanically polished ²⁾ , welds in as-welded condition	SJ, SL
Ra \leq 0.38 μ m (15 μ in) 1)	Mechanically polished ²⁾	SC, SF
Ra \leq 0.38 µm (15 µin) 1)	Mechanically polished ²⁾ , welds in as-welded condition	SK, SM
Ra \leq 0.38 μ m (15 μ in) 1)	Mechanical ²⁾ and electropolished	BC
Ra \leq 0.38 µm (15 µin) 1)	Mechanical ²⁾ and electropolished, welds in as-welded condition	BG

- 1) Ra according to ISO 21920
- 2) Except for inaccessible welds between pipe and manifold

Display and user interface

Operation concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnosis
- Expert level

Quick and safe commissioning

- Guided menus ("Make-it-run" wizards) for applications
- Menu guidance with brief descriptions of the individual parameter functions
- Access to the device via web server
- WLAN access to the device via mobile handheld terminal, tablet or smart phone

Reliable operation

- Operation in local language
- Uniform operating philosophy applied to device and operating tools
- If replacing electronic modules, transfer the device configuration via the integrated memory (HistoROM backup) which contains the process and measuring device data and the event logbook. No need to reconfigure.

Efficient diagnostics increase measurement reliability

- Troubleshooting measures can be called up via the device and in the operating tools
- Diverse simulation options, logbook for events that occur and optional line recorder functions

Languages

Can be operated in the following languages:

- Via local operation
 English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese,
 Japanese, Korean, Vietnamese, Czech, Swedish
- Via web browser
 English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese,
 Japanese, Vietnamese, Czech, Swedish
- Via "FieldCare", "DeviceCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese

Onsite operation

Via display module


Features:

- Order code for "Display; operation", option F "4-line, illuminated, graphic display; touch control"
- Order code for "Display; operation", option G "4-line, illuminated, graphic display; touch control + W/I A N"



Information about WLAN interface →

116



A0026785

50 Operation with touch control

Display elements

- 4-line, illuminated, graphic display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured

Operating elements

- External operation via touch control (3 optical keys) without opening the housing: ±, □, □
- Operating elements also accessible in the various zones of the hazardous area


108

Via remote display and operating module DKX001



The remote display and operating module DKX001 is available as an optional extra $\Rightarrow \triangleq 127$..

- The remote display and operating module DKX001 is only available for the following housing versions, order code for "Housing":
 - Option A "Aluminum, coated"
 - Option L "Cast, stainless"
- The measuring instrument is always supplied with a dummy cover when the remote display and operating module DKX001 is ordered directly with the measuring instrument. Display or operation at the transmitter is not possible in this case.
- If ordered subsequently, the remote display and operating module DKX001 may not be connected at the same time as the existing measuring instrument display module. Only one display or operation unit may be connected to the transmitter at any one time.



 \blacksquare 51 Operation via remote display and operating module DKX001

A0026786

Display and operating elements

The display and operating elements correspond to those of the display module $\rightarrow \stackrel{\triangle}{=} 108$.

Housing material

The housing material of the display and operating module DKX001 depends on the choice of transmitter housing material.

Transmitter housing		Remote display and operating module
Order code for "Housing"	Material	Material
Option A "Aluminum, coated"	AlSi10Mg, coated	AlSi10Mg, coated
Option L "Cast, stainless"	Cast stainless steel, 1.4409 (CF3M) similar to 316L	1.4409 (CF3M)

Cable entry

Corresponds to the choice of transmitter housing, order code for "Electrical connection".

Connecting cable

→ 🖺 50


Dimensions

→ 🗎 90

Remote operation


Via HART protocol

This communication interface is available in device versions with a HART output.



■ 52 Options for remote operation via HART protocol (active)

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 4 Commubox FXA 195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 Field Xpert SMT70
- 7 VIATOR Bluetooth modem with connecting cable
- 8 Transmitter




A00287

■ 53 Options for remote operation via HART protocol (passive)

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or computer with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA 195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 Field Xpert SMT70
- 9 VIATOR Bluetooth modem with connecting cable
- 10 Transmitter

Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




■ 54 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- 3 Industry network
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device

Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.



 \blacksquare 55 Options for remote operation via PROFIBUS DP network


- 1 Automation system
- 2 Computer with PROFIBUS network card
- *3 PROFIBUS DP network*
- 4 Measuring device

Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.

Endress+Hauser 111

A0020903




■ 56 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Segment coupler PROFIBUS DP/PA
- 5 PROFIBUS PA network
- 6 T-box
- 7 Measuring device

Via Modbus RS485 protocol

This communication interface is available in device versions with a Modbus RS485 output.




 \blacksquare 57 Options for remote operation via Modbus RS485 protocol (active)

- 1 Control system (e.g. PLC)
- 2 Computer with web browser (e.g. Microsoft Edge) to access the integrated device web server or with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 3 Transmitter

Via EtherNet/IP network

This communication interface is available in device versions with EtherNet/IP.

Star topology




₹ 58 Options for remote operation via EtherNet/IP network: star topology

- Automation system, e.g. "RSLogix" (Rockwell Automation)
- Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell 2 Automation) or with Electronic Data Sheet (EDS)
- Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer 3 with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- Measuring device

Ring topology

The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).




№ 59 Options for remote operation via EtherNet/IP network: ring topology

- Automation system, e.g. "RSLogix" (Rockwell Automation)
- Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell 2 Automation) or with Electronic Data Sheet (EDS)
- Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- Measuring device

Via PROFINET network

This communication interface is available in device versions with PROFINET.

Star topology




■ 60 Options for remote operation via PROFINET network: star topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Ring topology

The device is integrated via the terminal connection for signal transmission (output 1) and the service interface (CDI-RJ45).




■ 61 Options for remote operation via PROFINET network: ring topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

114 Endress+Hauser

A00337

Via APL network



A0046117

■ 62 Options for remote operation via APL network

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch, e.g. Scalance X204 (Siemens)
- 3 Computer with Web browser (e.g. Internet Explorer) for access to integrated Web server or computer with operating tool (e.g. FieldCare, DeviceCare with PROFINET COM DTM or SIMATIC PDM with FDI-Package)
- 4 APL power switch (optional)
- 5 APL field switch
- 6 Measuring device

Service interface

Via service interface (CDI-RJ45)


A point-to-point connection can be established to configure the device onsite. With the housing open, the connection is established directly via the service interface (CDI-RJ45) of the device.



An adapter for the RJ45 to the M12 plug is optionally available for the non-hazardous area:

Order code for "Accessories", option ${\bf NB}$: "Adapter RJ45 M12 (service interface)"

The adapter connects the service interface (CDI-RJ45) to an M12 plug mounted in the cable entry. The connection to the service interface can be established via an M12 plug without opening the device.




A002756

■ 63 Connection via service interface (CDI-RJ45)

- 1 Computer with web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated web server or with "FieldCare" operating tool, "DeviceCare" with COM DTM "CDI Communication TCP/IP" or Modbus DTM
- 2 Standard Ethernet connecting cable with RJ45 plug
- 3 Service interface (CDI-RJ45) of the measuring device with access to the integrated Web server

Via WLAN interface

The optional WLAN interface is available on the following device version: Order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN"



A003457

1 Transmitter with integrated WLAN antenna

Smart phone or tablet (e.g. Field Xpert SMT70)

- 2 Transmitter with external WLAN antenna
- 3 LED lit constantly: WLAN reception is enabled on measuring device
- 4 LED flashing: WLAN connection established between operating unit and measuring device
- 5 Computer with WLAN interface and web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device web server or with operating tool (e.g. FieldCare, DeviceCare)
- 6 Mobile handheld terminal with WLAN interface and web browser (e.g. Microsoft Internet Explorer, Microsoft Edge) for accessing the integrated device web server or operating tool (e.g. FieldCare, DeviceCare)

Function	WLAN: IEEE 802.11 b/g (2.4 GHz) Access Point with DHCP server (factory setting) Network
Encryption	WPA2-PSK AES-128 (in accordance with IEEE 802.11i)
Configurable WLAN channels	1 to 11
Degree of protection	IP67
Available antennas	 Internal antenna External antenna (optional) In the event of poor transmission/reception conditions at the place of installation. Available as an accessory . Only 1 antenna is active at any one time!
Range	 Internal antenna: typically 10 m (32 ft) External antenna: typically 50 m (164 ft)
Materials (external antenna)	 Antenna: ASA plastic (acrylonitrile styrene acrylate) and nickel-plated brass Adapter: Stainless steel and nickel-plated brass Cable: Polyethylene

Network integration


Network integration is only available for the HART communication protocol.

With the optional "OPC-UA Server" application package, the device can be integrated into an Ethernet network via the service interface (CDI-RJ45 and WLAN) and communicate with OPC-UA clients. If the device is used in this way, IT security must be considered.

Plug: Nickel-plated brassAngle bracket: Stainless steel

Transmitters with an Ex de approval may **not** be connected via the service interface (CDI-RJ45)! Order code for "Approval transmitter + sensor", options (Ex de): BA, BB, C1, C2, GA, GB, MA, MB, NA, NB

For permanent access to device data and for device configuration via the Web server, the device is incorporated directly in a network via the service interface (CDI-RJ45). In this way, the device can be accessed any time from the control station. The measured values are processed separately via the inputs and outputs through the automation system.



A0022618

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Ethernet switch
- 3 Edge Gateway
- 4 Cloud
- 5 Measuring device
- 6 Ethernet network
- 7 Measured values via inputs and outputs
- 8 Optional WLAN interface
- The optional WLAN interface is available on the following device version:
 Order code for "Display; operation", option **G** "4-line, backlit, graphic display; touch control + WLAN"

Supported operating tools

Different operating tools can be used for local or remote access to the measuring device. Depending on the operating tool used, access is possible with different operating units and via a variety of interfaces.

Supported operating tools	Operating unit	Interface	Additional information
Web browser	Notebook, PC or tablet with Web browser	 CDI-RJ45 service interface WLAN interface Ethernet-based fieldbus (EtherNet/IP, PROFINET) 	Special Documentation for device → 🖺 131
DeviceCare SFE100	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🖺 129
FieldCare SFE500	Notebook, PC or tablet with Microsoft Windows system	CDI-RJ45 service interfaceWLAN interfaceFieldbus protocol	→ 🖺 129

Supported operating tools	Operating unit	Interface	Additional information
Field Xpert	SMT70/77/50	 All fieldbus protocols WLAN interface Bluetooth CDI-RJ45 service interface 	Operating Instructions BA01202S Device description files: Use update function of handheld terminal
SmartBlue app	Smartphone or tablet with iOs or Android	WLAN	→ 🖺 129

- Other operating tools based on FDT technology with a device driver such as DTM/iDTM or DD/EDD can be used for device operation. These operating tools are available from the individual manufacturers. Integration into the following operating tools, among others, is supported:
 - FactoryTalk AssetCentre (FTAC) from Rockwell Automation → www.rockwellautomation.com
 - Process Device Manager (PDM) from Siemens → www.siemens.com
 - Asset Management Solutions (AMS) from Emerson → www.emersonprocess.com
 - FieldCommunicator 375/475 from Emerson → www.emersonprocess.com
 - Field Device Manager (FDM) from Honeywell → www.process.honeywell.com
 - FieldMate from Yokogawa → www.yokogawa.com
 - PACTWare → www.pactware.com

The related device description files are available: www.endress.com → Download Area

Web server

With the integrated web server, the device can be operated and configured via a web browser using Ethernet-APL, and via the service interface (CDI-RJ45) or WLAN interface. The structure of the operating menu is the same as for the local display. In addition to the measured values, status information on the device is displayed and can be used to monitor device health. Furthermore the device data can be managed and the network parameters can be configured.

Access to the network is required for the Ethernet-APL connection.

A device that has a WLAN interface (can be ordered as an option) is required for the WLAN connection: order code for "Display; operation", option G "4-line, illuminated; touch control + WLAN". The device acts as an Access Point and enables communication by computer or a mobile handheld terminal.

Supported functions

Data exchange between the operating unit (such as a notebook, for example,) and measuring instrument:

- Upload the configuration from the measuring instrument (XML format, configuration backup)
- Save the configuration to the measuring instrument (XML format, restore configuration)
- Export event list (.csv file)
- Export parameter settings (.csv file or PDF file, document the measuring point configuration)
- Export the Heartbeat Technology verification report (PDF file, only available with the Heartbeat Verification → ≅ 125 application package)
- $\ \ \blacksquare$ Flash firmware version for device firmware upgrade, for example
- Download driver for system integration

HistoROM data management

The measuring device features HistoROM data management. HistoROM data management comprises both the storage and import/export of key device and process data, making operation and servicing far more reliable, secure and efficient.

When the device is delivered, the factory settings of the configuration data are stored as a backup in the device memory. This memory can be overwritten with an updated data record, for example after commissioning.

Additional information on the data storage concept

There are different types of data storage units in which device data are stored and used by the device:

	HistoROM backup	T-DAT	S-DAT
Available data	 Event logbook, e.g. diagnostic events Parameter data record backup Device firmware package Driver for system integration for exporting via web server, e.g.: GSD for PROFIBUS DP GSD for PROFIBUS PA GSDML for PROFINET EDS for EtherNet/IP DD for FOUNDATION Fieldbus 	Measured value logging ("Extended HistoROM" order option) Current parameter data record (used by firmware at run time) Indicator (minimum/maximum values) Totalizer value	 Sensor data: e.g. nominal diameter Serial number Calibration data Device configuration (e.g. SW options, fixed I/O or multi I/O)
Storage location	Fixed on the user interface PC board in the connection compartment	Can be plugged into the user interface PC board in the connection compartment	In the sensor plug in the transmitter neck part

Data backup

Automatic

- The most important device data (sensor and transmitter) are automatically saved in the DAT modules
- If the transmitter or measuring device is replaced: once the T-DAT containing the previous device data has been exchanged, the new measuring device is ready for operation again immediately without any errors
- If exchanging the electronics module (e.g. I/O electronics module): Once the electronics module has been replaced, the software of the module is compared against the current device firmware. The module software is upgraded or downgraded where necessary. The electronics module is available for use immediately afterwards and no compatibility problems occur.

Manual

Additional parameter data record (complete parameter settings) in the integrated device memory HistoROM backup for:

- Data backup function
 - Backup and subsequent restoration of a device configuration in the device memory HistoROM backup
- Data comparison function
 - $\label{thm:comparison} Comparison of the current device configuration with the device configuration saved in the device memory HistoROM backup$

Data transmission

Manual

- Transfer of a device configuration to another device using the export function of the specific operating tool, e.g. with FieldCare, DeviceCare or Web server: to duplicate the configuration or to store in an archive (e.g. for backup purposes)
- Transmission of the drivers for system integration via Web server, e.g.:
 - GSD for PROFIBUS DP
 - GSD for PROFIBUS PA
 - GSDML for PROFINET
 - EDS for EtherNet/IP
 - DD for FOUNDATION Fieldbus

Event list

Automatic

- Chronological display of up to 20 event messages in the events list
- If the Extended HistoROM application package (order option) is enabled: up to 100 event messages are displayed in the events list along with a time stamp, plain text description and remedial measures
- The events list can be exported and displayed via a variety of interfaces and operating tools e.g. DeviceCare, FieldCare or Web server

Data logging

Manual

If the **Extended HistoROM** application package (order option) is enabled:

- Recording of 1 to 4 channels of up to 1000 measured values (up to 250 measured values per channel)
- User configurable recording interval
- Export the measured value log via a variety of interfaces and operating tools e.g. FieldCare, DeviceCare or web server

Certificates and approvals

Current certificates and approvals for the product are available at www.endress.com on the relevant product page:

- 1. Select the product using the filters and search field.
- 2. Open the product page.
- 3. Select **Downloads**.

CE mark

The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.

Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

UKCA marking

The device meets the legal requirements of the applicable UK regulations (Statutory Instruments). These are listed in the UKCA Declaration of Conformity along with the designated standards. By selecting the order option for UKCA marking, Endress+Hauser confirms a successful evaluation and testing of the device by affixing the UKCA mark.

Contact address Endress+Hauser UK:

Endress+Hauser Ltd.

Floats Road

Manchester M23 9NF

United Kingdom

www.uk.endress.com

RCM marking

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the name plate

Devices with the order code for "Approval; transmitter + sensor", option BA, BB, BC or BD have equipment protection level (EPL) Ga/Gb (Zone 0 in the measuring tube).



The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.

ATEX/IECEx

Currently, the following versions for use in hazardous areas are available:

Ex db eb

Category	Type of protection
II1/2G	Ex db eb ia IIC T6T1 Ga/Gb Ex db eb ia IIB T6T1 Ga/Gb
II2G	Ex db eb ia IIC T6T1 Gb Ex db eb ia IIB T6T1 Gb

Ex db

Category	Type of protection
II1/2G	Ex db ia IIC T6T1 Ga/Gb Ex db ia IIB T6T1 Ga/Gb
II2G	Ex db ia IIC T6T1 Gb Ex db ia IIB T6T1 Gb

Ех ес

Category	Type of protection
II3G	Ex ec IIC T5T1 Gc

Ex tb

Category	Type of protection	
II2D	Ex tb IIIC T** °C Db	

$_{C}CSA_{US}$

Currently, the following versions for use in hazardous areas are available:

IS (Ex i) and XP (Ex d)

- Class I, II, III Division 1 Groups A-G
- Class I, II, III Division 1 Groups C-G

NI (Ex ec)

Class I Division 2 Groups A - D

Ex db eb

- Class I, Zone 1 AEx/ Ex db eb ia IIC T6...T1 Ga/Gb Class I, Zone 1 AEx/ Ex db eb ia IIB T6...T1 Ga/Gb
- Class I, Zone 1 AEx/Ex db eb ia IIC T6...T1 Gb Class I, Zone 1 AEx/Ex db eb ia IIB T6...T1 Gb

Ex db

- Class I, Zone 1 AEx/ Ex db ia IIC T6...T1 Ga/Gb Class I, Zone 1 AEx/ Ex db ia IIB T6...T1 Ga/Gb
- Class I, Zone 1 AEx/ Ex db ia IIC T6...T1 Gb Class I, Zone 1 AEx/ Ex db ia IIB T6...T1 Gb

Ex ec

Class I, Zone 2 AEx/ Ex ec IIC T5...T1 Gc

Ex tb

Zone 21 AEx/ Ex tb IIIC T** $^{\circ}$ C Db

Hygienic compatibility

- 3-A approval
 - Only measuring instruments with the order code for "Additional approval", option LP "3A" have 3-A approval.
 - The 3-A approval refers to the measuring instrument.
 - When installing the measuring instrument, ensure that no liquid can accumulate on the outside
 of the measuring instrument.
 - A remote display module must be installed in accordance with the 3-A Standard.
 - Accessories (e.g. heating jacket, weather protection cover, wall holder unit) must be installed in accordance with the 3-A Standard.
 - Each accessory can be cleaned. Disassembly may be necessary under certain circumstances.
- EHEDG-tested

Only devices with the order code for "Additional approval", option LT "EHEDG" have been tested and meet the requirements of the EHEDG.

To meet the requirements for EHEDG certification, the device must be used with process connections in accordance with the EHEDG position paper entitled "Easy cleanable Pipe couplings and Process connections" (www.ehedq.org).

To meet the requirements for EHEDG certification, the device must be installed in a position that ensures drainability.

- FDA
- Food Contact Materials Regulation (EC) 1935/2004
- i

HART certification

HART interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability)

FOUNDATION Fieldbus certification

FOUNDATION Fieldbus interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified in accordance with FOUNDATION Fieldbus H1
- Interoperability Test Kit (ITK), revision version 6.2.0 (certificate available on request)
- Physical Layer Conformance Test
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFIBUS

PROFIBUS interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V./ PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

EtherNet/IP certification

The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with the ODVA Conformance Test
- EtherNet/IP Performance Test
- EtherNet/IP PlugFest compliance
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFINET

PROFINET interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e.V. / PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
 - Test specification for PROFINET devices
 - PROFINET Security Level 2 Netload Class 2 0 Mbps
- The device can also be operated with certified devices of other manufacturers (interoperability)
- The device supports PROFINET S2 system redundancy.

PROFINET with Ethernet-APL certification

PROFINET interface

The measuring device is certified and registered by the PNO (PROFIBUS Nutzerorganisation e. V./ PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
 - Test specification for PROFINET devices
 - PROFINET PA Profile 4
 - PROFINET netload robustness Class 2 10 Mbit/s
 - APL conformance test
- The device can also be operated with certified devices of other manufacturers (interoperability)
- The device supports PROFINET S2 system redundancy.

Pressure Equipment Directive

The measuring devices can be ordered with or without PED or PESR. If a device with PED or PESR is required, this must be ordered explicitly. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary. A UK order option must be selected for PESR under the order code for "Approvals".

- With the marking
 - a) PED/G1/x (x = category) or
 - b) PESR/G1/x (x = category)
 - on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements"
 - a) specified in Annex I of the Pressure Equipment Directive 2014/68/EU or
 - b) Schedule 2 of Statutory Instruments 2016 No. 1105.
- Devices bearing this marking (PED or PESR) are suitable for the following types of medium:
 - Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to 0.5 bar (7.3 psi)
 - Unstable gases
- Devices not bearing this marking (without PED or PESR) are designed and manufactured according
 to sound engineering practice. They meet the requirements of
 - a) Art. 4 Para. 3 of the Pressure Equipment Directive 2014/68/EU or
 - b) Part 1, Para. 8 of Statutory Instruments 2016 No. 1105.

The scope of application is indicated

- a) in diagrams 6 to 9 in Annex II of the Pressure Equipment Directive 2014/68/EU or
- b) Schedule 3, Para. 2 of Statutory Instruments 2016 No. 1105.

Radio approval

The measuring device has radio approval.



For detailed information on the radio approval, see the Special Documentation $\rightarrow \implies 131$

Measuring instrument approval

The measuring device is (optionally) approved as a gas meter (MI-002) or component in measuring systems (MI-005) in service subject to legal metrological control in accordance with the European Measuring Instruments Directive 2014/32/EU (MID).

The measuring device is qualified to OIML R117 or OIML R137 OIML R117 and has an OIML Certificate of Conformity (optional).

Additional certification

CRN approval

Some device versions have CRN approval. A CRN-approved process connection with a CSA approval must be ordered for a CRN-approved device.

Tests and certificates

- ISO 23277 ZG2x (PT)+ISO 10675-1 ZG1 (RT) measuring pipe (PT) + process connection (RT) weld seam, Heartbeat Technology verification report
- Penetrant + radiographic testing ASME B31.3 NFS(RT) measuring pipe (PT) + process connection (RT) weld seam, Heartbeat Technology verification report
- Penetrant + radiographic testing ASME VIII Div.1(RT) measuring pipe (PT) + process connection (RT) weld seam, Heartbeat Technology verification report
- Visual+penetrant+radiographic testing NORSOK M-601 (RT) measuring pipe (VT+PT) +process connection (VT+RT) weld seam, Heartbeat Technology verification report
- ISO 23277 ZG2x (PT)+ISO 10675-1 ZG1 (DR) measuring pipe (PT) + process connection (DR) weld seam, Heartbeat Technology verification report

- Penetrant + radiographic testing ASME B31.3 NFS(DR) measuring pipe (PT) + process connection (DR) weld seam, Heartbeat Technology verification report
- Penetrant +radiographic testing ASME VIII Div.1(DR) measuring pipe (PT) + process connection (DR) weld seam, Heartbeat Technology verification report
- Visual +penetrant+radiographic testing NORSOK M-601 (DR) measuring pipe (VT+PT) +process connection (VT+DR) weld seam, Heartbeat Technology verification report

Testing of welded connections

Option	Test standard			Component		
	ISO 23277 AL2x (PT) ISO 10675-1 AL1 (RT, DR)	ASME B31.3 NFS	ASME VIII Div.1 Appx. 4+8	NORSOK M-601	Measuring pipe	Process connection
KF	х				PT	RT
KK		х			PT	RT
KP			х		PT	RT
KR				х	VT, PT	VT, RT
K1	х				PT	DR
K2		х			PT	DR
КЗ			х		PT	DR
K4				Х	VT, PT	VT, DR

PT = penetrant testing, RT = radiographic testing, VT = visual testing, DR = digital radiography All options with test report

External standards and guidelines

■ EN 60529

Degrees of protection provided by enclosures (IP code)

■ IEC/EN 60068-2-6

Environmental influences: Test procedure - Test Fc: vibrate (sinusoidal).

■ IEC/EN 60068-2-31

Environmental influences: Test procedure - Test Ec: shocks due to rough handling, primarily for devices.

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements

■ EN 61326-1/-2-3

EMC requirements for electrical equipment for measurement, control and laboratory use

■ NAMUR NE 21

Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment

■ NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

■ NAMUR NE 80

The application of the pressure equipment directive to process control devices

■ NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices

■ NAMUR NE 107

Self-monitoring and diagnosis of field devices

■ NAMUR NE 131

Requirements for field devices for standard applications

■ NAMUR NE 132

Coriolis mass meter

■ NACE MR0103

Materials resistant to sulfide stress cracking in corrosive petroleum refining environments.

- NACE MR0175/ISO 15156-1
 - Materials for use in H2S-containing Environments in Oil and Gas Production.
- ETSI EN 300 328
 - Guidelines for 2.4 GHz radio components.
- EN 301489

Electromagnetic compatibility and radio spectrum matters (ERM).

Ordering information

Detailed ordering information is available from your nearest sales organization www.addresses.endress.com or in the Product Configurator at www.endress.com:

- 1. Select the product using the filters and search field.
- 2. Open the product page.
- 3. Select Configuration.

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.



Detailed information on the application packages:

Special Documentation $\rightarrow \implies 131$

Diagnostic functionality

Order code for "Application package", option EA "Extended HistoROM"

Comprises extended functions concerning the event log and the activation of the measured value memory.

Event log:

Memory volume is extended from 20 message entries (standard version) to up to 100 entries.

Data logging (line recorder):

- Memory capacity for up to 1000 measured values is activated.
- 250 measured values can be output via each of the 4 memory channels. The recording interval can
 be defined and configured by the user.
- Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server.



For detailed information, see the Operating Instructions for the device.

Heartbeat Technology

Order code for "Application package", option EB "Heartbeat Verification + Monitoring"

Heartbeat Verification

Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment".

- Functional testing in the installed state without interrupting the process.
- Traceable verification results on request, including a report.
- Simple testing process via local operation or other operating interfaces.
- Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.
- Extension of calibration intervals according to operator's risk assessment.

Heartbeat Monitoring

Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to:

- Draw conclusions using these data and other information about the impact process influences (e.g. corrosion, abrasion, buildup etc.) have on the measuring performance over time.
- Schedule servicing in time.
- Monitor the process or product quality, e.g. gas pockets .



For detailed information, see the Special Documentation for the device.

Concentration measurement

Order code for "Application package", option ED "Concentration"

Calculation and outputting of fluid concentrations.

The measured density is converted to the concentration of a substance of a binary mixture using the "Concentration" application package:

- Choice of predefined fluids (e.g. various sugar solutions, acids, alkalis, salts, ethanol etc.).
- Common or user-defined units ("Brix, "Plato, % mass, % volume, mol/l etc.) for standard applications.
- Concentration calculation from user-defined tables.



For detailed information, see the Special Documentation for the device.

Special density

Order code for "Application package", option EE "Special density"

Many applications use density as a key measured value for monitoring quality or controlling processes. The measuring instrument measures the density of the fluid as standard and makes this value available to the control system.

The "Special Density" application package offers high-precision density measurement over a wide density and temperature range particularly for applications subject to varying process conditions.

The calibration certificate supplied contains the following information:

- Density performance in air
- Density performance in liquids with different density
- Density performance in water with different temperatures



For detailed information, see the Operating Instructions for the device.

Extended density

Order code for "Application package", option E1 "Extended density"

For volume-based applications, the device can calculate and output a volume flow rate by dividing the mass flow rate by the measured density.

This application package is the standard calibration for custody transfer applications according to national and international standards (e.g. OIML, MID). It is recommended for volume-based fiscal dosing applications over a wide temperature range.

The calibration certificate supplied describes the density performance in air and water at various temperatures in detail.



For detailed information, see the Operating Instructions for the device.

Petroleum

Order code for "Application package", option EJ "Petroleum"

The most important parameters for the Oil & Gas Industry can be calculated and displayed with this application package.

- Corrected volume flow and calculated reference density in accordance with the "API Manual of Petroleum Measurement Standards, Chapter 11.1"
- Water content, based on density measurement
- Weighted mean of the density and temperature



For detailed information, see the Special Documentation for the device.

Petroleum & locking function

Order code for "Application package", option EM "Petroleum & locking function"

The most important parameters for the Oil & Gas Industry can be calculated and displayed with this application package. It is also possible to lock the settings.

- Corrected volume flow and calculated reference density in accordance with the "API Manual of Petroleum Measurement Standards, Chapter 11.1"
- Water content, based on density measurement
- Weighted mean of the density and temperature



For detailed information, see the Special Documentation for the device.

OPC-UA Server

Order code for "Application package", option EL "OPC-UA Server"

The application package provides an integrated OPC-UA server for comprehensive device services for IoT and SCADA applications.



For detailed information, see the Special Documentation for the device.

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the transmitter

Accessories	Description
Proline 300 transmitter	Transmitter for replacement or storage. Use the order code to define the following specifications: Approvals Output Input Display/operation Housing Software Order code: 8X3BXX Installation Instructions EA01200D

Remote display and	The section of the se
operating module DKX001	 If ordered directly with the measuring device: Order code for "Display; operation", option O "Remote display 4-line, illuminated; 10 m (30 ft) cable; touch control" If ordered separately: Measuring device: order code for "Display; operation", option M "W/o, prepared for remote display" DKX001: Via the separate product structure DKX001 If ordered subsequently: DKX001: Via the separate product structure DKX001
	Mounting bracket for DKX001 ■ If ordered directly: order code for "Accessory enclosed", option RA "Mounting bracket, pipe 1/2" ■ If ordered subsequently: order number: 71340960
	Connecting cable (replacement cable) Via the separate product structure: DKX002
	Further information on display and operating module DKX001 \rightarrow 🗎 109.
	Special Documentation SD01763D
External WLAN antenna	External WLAN antenna with 1.5 m (59.1 in) connecting cable and two angle brackets. Order code for "Accessory enclosed", option P8 "Wireless antenna wide area".
	The external WLAN antenna is not suitable for use in hygienic applications.
	• Additional information regarding the WLAN interface $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $
	Order number: 71351317
	Installation Instructions EA01238D
Weather protection cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight.
	Order number: 71343505
	Installation Instructions EA01160D

For the sensor

Accessories	Description
Heating jacket	Is used to stabilize the temperature of the fluids in the sensor. Water, water vapor and other non-corrosive liquids are permitted for use as fluids.
	If using oil as a heating medium, please consult with Endress+Hauser.
	Heating jackets cannot be used with sensors fitted with a rupture disk. Use the order code with the product root DK8003.
	Special Documentation SD02156D

Communication-specific accessories

Accessories	Description			
Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB port. Technical Information TI00404F			
HART loop converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog curre signals or limit values.			
	Technical Information TI00429FOperating Instructions BA00371F			

Fieldgate FXA42	Transmission of the measured values of connected 4 to 20 mA analog measuring instruments, as well as digital measuring instruments Technical Information TI01297S Operating Instructions BA01778S Product page: www.endress.com/fxa42
Field Xpert SMT50	The Field Xpert SMT50 tablet PC for device configuration enables mobile plant
Their Apert Sivi 20	asset management in the non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage field instruments throughout their entire life cycle.
	 Technical Information TI01555S Operating Instructions BA02053S Product page: www.endress.com/smt50
Field Xpert SMT70	The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage field instruments with a digital communication interface and to record progress. This tablet PC is designed as an all-in-one solution with a preinstalled driver library and is an easy-to-use, touch-sensitive tool which can be used to manage the field instruments throughout their entire life cycle.
	 Technical Information TI01342S Operating Instructions BA01709S Product page: www.endress.com/smt70
Field Xpert SMT77	The Field Xpert SMT77 tablet PC for device configuration enables mobile plant asset management in areas categorized as Ex Zone 1.
	 Technical Information TI01418S Operating Instructions BA01923S Product page: www.endress.com/smt77

Service-specific accessories

Accessories	Description
Applicator	Software for selecting and sizing Endress+Hauser measuring instruments: Choice of measuring instruments for industrial requirements Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and measurement accuracy. Graphic display of the calculation results Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project. Applicator is available: Via the Internet: https://portal.endress.com/webapp/applicator
Netilion	lloT ecosystem: Unlock knowledge With the Netilion IIoT ecosystem,Endress+Hauser allows you to optimize your plant performance, digitize workflows, share knowledge, and enhance collaboration. Drawing upon decades of experience in process automation, Endress+Hauser offers the process industry an IIoT ecosystem designed to effortlessly extract insights from data. These insights allow process optimization, leading to increased plant availability, efficiency, and reliability - ultimately resulting in a more profitable plant. www.netilion.endress.com
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all intelligent field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition. Operating Instructions BA00027S and BA00059S
DeviceCare	Tool to connect and configure Endress+Hauser field devices. Innovation brochure IN01047S

System component	ES.
------------------	-----

Accessories	Description
Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.
	 Technical Information TI00133R Operating Instructions BA00247R
Cerabar M	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.
	 Technical Information TI00426P and TI00436P Operating Instructions BA00200P and BA00382P
Cerabar S	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value. Technical Information TI00383P Operating Instructions BA00271P
iTEMP	The temperature transmitters can be used in all applications and are suitable for
	the measurement of gases, steam and liquids. They can be used to read in the medium temperature.
	"Fields of Activity" document FA00006T

Supplemental documentation

- - For an overview of the scope of the associated Technical Documentation, refer to the following:
 - Device Viewer (www.endress.com/deviceviewer): Enter the serial number from the nameplate
 - Endress+Hauser Operations app: Enter serial number from nameplate or scan matrix code on nameplate.

Standard documentation

Supplementary information on the semi-standard options is available in the relevant Special Documentation in the TSP database.

Brief Operating Instructions

Brief Operating Instructions for the sensor

Measuring instrument	Documentation code
Proline Promass F	KA01261D

Brief Operating Instructions for the transmitter

	Documentation code							
Measuring device	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Proline 300	KA01309D	KA01229D	KA01227D	KA01386D	KA01311D	KA01339D	KA01341D	KA01517D

Operating Instructions

Measuring device	Documentation code							
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Promass F 300	BA01485D	BA01518D	BA01507D	BA01850D	BA01496D	BA01728D	BA01739D	BA01739D

Description of Device Parameters

	Documentation code							
Measuring device	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	EtherNet/IP	PROFINET	PROFINET with Ethernet- APL
Promass 300	GP01057D	GP01094D	GP01058D	GP01134D	GP01059D	GP01114D	GP01115D	GP01168D

Supplementary devicedependent documentation Safety instructions

Safety instructions for electrical equipment for hazardous areas. \\

Contents	Documentation code
ATEX/IECEx Ex d/Ex de	XA01405D
ATEX/IECEx Ex ec	XA01439D
cCSAus XP	XA01373D
cCSAus Ex d/ Ex de	XA01372D
cCSAus Ex nA	XA01507D
INMETRO Ex d/Ex de	XA01468D
INMETRO Ex ec	XA01470D
NEPSI Ex d/Ex de	XA01469D
NEPSI Ex nA	XA01471D
EAC Ex d/Ex de	XA01656D
EAC Ex nA	XA01657D
JPN Ex d	XA01778D

Remote display and operating module DKX001

Contents	Documentation code
ATEX/IECEx Ex i	XA01494D
ATEX/IECEx Ex ec	XA01498D
cCSAus IS	XA01499D
cCSAus Ex nA	XA01513D
INMETRO Ex i	XA01500D
INMETRO Ex ec	XA01501D
NEPSI Ex i	XA01502D
NEPSI Ex nA	XA01503D

Functional Safety Manual

Contents	Documentation code
Proline Promass 300	SD01727D

Special documentation

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01614D
Remote display and operating module DKX001	SD01763D

Contents	Documentation code
Radio approvals for WLAN interface for A309/A310 display module	SD01793D
OPC-UA server ¹⁾	SD02039D

1) This Special Documentation is only available for device versions with a HART output.

Contents	Documentation code							
	HART	FOUNDATIO N Fieldbus	PROFIBUS PA	PROFIBUS DP	Modbus RS485	PROFINET	Ethernet/IP	PROFINET over Ethernet- APL
Web server	SD01662D	SD01665D	SD01664D	SD02226D	SD01663D	SD01969D	SD01968D	SD02762D
Heartbeat Technology	SD01642D	SD01696D	SD01698D	SD02202D	SD01697D	SD01988D	SD01982	SD02731D
Concentration measurement	SD01644D	SD01706D	SD01708D	SD02212D	SD01707D	SD02005D	SD02004D	SD02735D
Petroleum	SD02097D	-	SD02291D	SD02216D	SD02098D	SD02099D	SD02096D	SD02739D
Petroleum & locking function	SD02499D	-	-	-	SD02500D	-	-	SD02739D
Gas fraction handler	SD02584D	-	-	-	SD02584D	SD02584D	-	SD02584D
Custody transfer	SD01688D	_	_	_	SD01689D	_	_	_

Installation instructions

Contents	Note
1 1	Documentation code: specified for each individual accessory $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas USA

PROFIBUS®

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

FOUNDATION™ Fieldbus

Registration-pending trademark of the FieldComm Group, Austin, Texas, USA

Modbus[®]

Registered trademark of SCHNEIDER AUTOMATION, INC.

EtherNet/IP™

Trademark of ODVA, Inc.

Ethernet-APL $^{\text{TM}}$

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

PROFINET®

Registered trademark of the PROFIBUS Nutzerorganisation e.V. (PROFIBUS User Organization), Karlsruhe, Germany

TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA





www.addresses.endress.com